


Overview

KEMET's X8L dielectric features a 150°C maximum operating temperature and is considered "general purpose high temperature." These components are fixed, ceramic dielectric capacitors suited for high temperature bypass and decoupling applications or frequency discriminating circuits where Q and stability of capacitance characteristics are not critical. X8L exhibits a predictable change in capacitance with respect to time and voltage and boasts a minimal change in capacitance with reference to ambient temperature up to 125°C. Beyond 125°C X8L displays a wider variation in capacitance. Capacitance change is limited to ±15% from -55°C to +125°C and +15, -40% from 125°C to 150°C.

Driven by the demand for a more robust and reliable component, X8L dielectric capacitors were developed for critical applications where reliability at higher operating temperatures are a concern. These capacitors are widely used in automotive circuits as well as general high temperature applications. Concerned with flex cracks resulting from excessive tensile and shear stresses produced during board flexure and thermal cycling? These devices are available with KEMET's Flexible termination technology which inhibits the transfer of board stress to the rigid ceramic body, therefore mitigating flex cracks which can result in low IR or short circuit failures. Although flexible termination technology does not eliminate the potential for mechanical damage that may propagate during extreme environmental and handling conditions, it does provide superior flex performance over standard termination systems.

In addition to commercial grade, automotive grade devices are available and meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.



С	1210	X	106	K	8	N	Α	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series ¹	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric Failure Dielectric Rate/ Design		Termination Finish ²	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210	C = Standard X = Flexible Termination	Two significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50	N = X8L	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Ordering Information

¹ The flexible termination option is not available on EIA 0402 case size product. "C" must be used in the 6th character position when ordering this case size.

²Additional termination finish options may be available. Contact KEMET for details.

² SnPb termination finish option is not available on Automotive Grade product.



Packaging C-Spec Ordering Options Table

Packaging Type	Packaging/Grade Ordering Code (C-Spec)							
Commercial Grade ¹								
Bulk Bag	Not Required (Blank)							
7" Reel/Unmarked	TU							
13" Reel/Unmarked	7411 (EIA 0603 and smaller case sizes) 7210 (EIA 0805 and larger case sizes)							
7" Reel/Marked	ТМ							
13" Reel/Marked	7040 (EIA 0603 and smaller case sizes) 7215 (EIA 0805 and larger case sizes)							
7" Reel/Unmarked/2 mm pitch ²	7081							
13" Reel/Unmarked/2 mm pitch ²	7082							
Automoti	ve Grade ³							
7" Reel	AUTO							
13" Reel/Unmarked	AUT07411 (EIA 0603 and smaller case sizes) AUT07210 (EIA 0805 and larger case sizes)							
7" Reel/Unmarked/2 mm pitch ²	3190							
13" Reel/Unmarked/2 mm pitch ²	3191							

¹ Default packaging is "Bulk Bag". An ordering code C-Spec is not required for "Bulk Bag" packaging.

¹ The terms "Marked" and "Unmarked" pertain to laser marking option of capacitors. All packaging options labeled as "Unmarked" will contain capacitors that have not been laser marked.

- ² The 2 mm pitch option allows for double the packaging quantity of capacitors on a given reel size. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".
- ³ Reeling tape options (Paper or Plastic) are dependent on capacitor case size (L" x W") and thickness dimension. See "Chip Thickness/Tape & Reel Packaging Quantities" and "Tape & Reel Packaging Information".

³ For additional Information regarding "AUTO" C-Spec options, see "Automotive C-Spec Information".

³ All Automotive packaging C-Specs listed exclude the option to laser mark components. Please contact KEMET if you require a laser marked option. For more information see "Capacitor Marking".

Benefits

- -55°C to +150°C operating temperature range
- · Lead (Pb)-free, RoHS and REACH compliant
- EIA 0402, 0603, 0805, 1206, and 1210 case sizes
- DC voltage ratings of 10 V, 16 V, 25 V, and 50 V
- Capacitance offerings ranging from 0.012 μ F to 10 μ F
- Available capacitance tolerances of ±5%, ±10%, and ±20%
- Commercial & Automotive (AEC-Q200) grades available
- · Non-polar device, minimizing installation concerns
- 100% pure matte tin-plated termination finish allowing for excellent solderability
- SnPb termination finish option available upon request (5% Pb minimum)
- · Flexible termination option available upon request

Applications

Typical applications include use in extreme environments such as down-hole oil exploration, under-hood automotive, military and aerospace.



Automotive C-Spec Information

KEMET Automotive Grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. These products are supported by a Product Change Notification (PCN) and Production Part Approval Process warrant (PPAP).

Automotive products offered through our distribution channel have been assigned an inclusive ordering code C-Spec, "AUTO". This C-Spec was developed in order to better serve small and medium sized companies that prefer an automotive grade component without the requirement to submit a customer Source Controlled Drawing (SCD) or specification for review by a KEMET engineering specialist. This C-Spec is therefore not intended for use by KEMET's OEM Automotive customers and are not granted the same "privileges" as other automotive C-Specs. Customer PCN approval and PPAP request levels are limited (see details below).

Product Change Notification (PCN)

The KEMET Product Change Notification system is used to communicate primarily the following types of changes:

- Product/process changes that affect product form, fit, function, and/or reliability
- Changes in manufacturing site
- Product obsolescence

KEMET Automotive	Customer Notifica	tion due to:	Days prior to		
C-Spec	Process/Product change	Obsolescence*	implementation		
KEMET assigned ¹	Yes (with approval and sign off)	Yes	180 days Minimum		
AUTO	Yes (without approval)	Yes	90 days Minimum		

¹ KEMET assigned C-Specs require the submittal of a customer SCD or customer specification for review. For additional information contact KEMET.

Production Part Approval Process (PPAP)

The purpose of the Production Part Approval Process is:

- To ensure that supplier can meet the manufacturability and quality requirements for the purchased parts.
- To provide the evidence that all customer engineering design record and specification requirements are properly understood and

fulfilled by the manufacturing organization.

• To demonstrate that the established manufacturing process has the potential to produce the part

KEMET Automotive	PPAP (Product Part Approval Process) Level											
C-Spec	1	2	3	4	5							
KEMET assigned ¹	•	•	•	•	•							
AUTO	0		0									


¹ KEMET assigned C-Specs require the submittal of a customer SCD or customer specification for review. For additional information contact KEMET.

• Part Number specific PPAP available

Product family PPAP only



Dimensions – Standard Termination – Millimeters (Inches)



EIA Size Code	Metric Size Code			T Thickness	B Bandwidth	S Separation Minimum	Mounting Technique	
0402	1005	1.00 (0.040) ±0.05 (0.002)	0.50 (0.020) ±0.05 (0.002)		0.30 (0.012) ±0.10 (0.004)	0.30 (0.012)	Solder Reflow Only	
0603	1608	1.60 (0.063) ±0.15 (0.006)	0.80 (0.032) ±0.15 (0.006)		0.35 (0.014) ±0.15 (0.006)	0.70 (0.028)	Solder Wave or Solder Reflow	
0805	2012	2.00 (0.079) ±0.20 (0.008)	1.25 (0.049) ±0.20 (0.008)	See Table 2 for Thickness	0.50 (0.02) ±0.25 (0.010)	0.75 (0.030)		
1206	3216	3.20 (0.126) ±0.20 (0.008)	1.60 (0.063) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)	N1 / A		
1210	1210 3225		2.50 (0.098) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)	N/A	Solder Reflow Only	

Dimensions – Flexible Termination – Millimeters (Inches)

EIA Size Code	Metric Size Code	L Length	W Width	T Thickness	B Bandwidth	S Separation Minimum	Mounting Technique	
0603	1608	1.60 (0.063) ±0.17 (0.007)	0.80 (0.032) ±0.15 (0.006)		0.45 (0.018) ±0.15 (0.006)	0.58 (0.023)	O a la la an Warra	
0805	2012	2.00 (0.079) ±0.30 (0.012)	1.25 (0.049) ±0.30 (0.012)	See Table 2 for	0.50 (0.020) ±0.25 (0.010)	0.75 (0.030)	Solder Wave or Solder Reflow	
1206	3216	3.30 (0.130) ±0.40 (0.016)	1.60 (0.063) ±0.35 (0.013)	Thickness	0.60 (0.024) ±0.25 (0.010)	N1/A	Soluei Rellow	
1210	3225	3.30 (0.130) ±0.40 (0.016)	2.60 (0.102) ±0.30(0.012)		0.60 (0.024) ±0.25 (0.010)	N/A	Solder Reflow Only	



Qualification/Certification

Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance & Reliability.

Automotive Grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. For additional information regarding the Automotive Electronics Council and AEC-Q200, please visit their website at www.aecouncil.com.

Environmental Compliance

Lead (Pb)-free, RoHS, and REACH compliant without exemptions (excluding SnPb termination finish option).

Electrical Parameters/Characteristics

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +150°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±15% (-55°C to 125°C), +15, -40% (125°C to 150°C)
¹ Aging Rate (Maximum % Capacitance Loss/Decade Hour)	3.0%
² Dielectric Withstanding Voltage (DWV)	250% of rated voltage (5±1 seconds and charge/discharge not exceeding 50 mA)
³ Dissipation Factor (DF) Maximum Limit at 25°C	3.5% (≤ 16V) and 2.5% (≥ 25V)
⁴ Insulation Resistance (IR) Minimum Limit at 25°C	500 megohm microfarads or 10 GΩ (Rated voltage applied for 120±5 seconds at 25°C)

¹Regarding Aging Rate: Capacitance measurements (including tolerance) are indexed to a referee time of 1,000 hours.

²DWV is the voltage a capacitor can withstand (survive) for a short period of time. It exceeds the nominal and continuous working voltage of the capacitor.

³ Capacitance and dissipation factor (DF) measured under the following conditions:

1kHz ± 50Hz and 1.0 ± 0.2 Vrms if capacitance ≤10 μ F

120Hz \pm 10Hz and 0.5 \pm 0.1 Vrms if capacitance >10 μF

⁴ To obtain IR limit, divide $M\Omega$ - μ F value by the capacitance and compare to G Ω limit. Select the lower of the two limits.

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 & Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON".



Post Environmental Limits

	High Temperature Life, Biased Humidity, Moisture Resistance											
Dielectric	Rated DC Voltage	Capacitance Value	Dissipation Factor (Maximum %)	Capacitance Shift	Insulation Resistance							
VOL	≥ 25	All	3.0	100%	10% of Initial							
X8L	≤ 16	All	5.0	±20%	Limit							

Insulation Resistance Limit Table (X8L Dielectric)

EIA Case Size	1,000 Megohm Microfarads or 100 GΩ	500 Megohm Microfarads or 10 GΩ					
0201	N/A	ALL					
0402	< .012 µF	≥ .012 µF					
0603	< .047 µF	≥ .047 µF					
0805	< 0.15 µF	≥ 0.15 µF					
1206	< 0.47 µF	≥ 0.47 µF					
1210	< 0.39 µF	≥ 0.39 µF					
1808	ALL	N/A					
1812	< 2.2 µF	≥ 2.2 µF					
1825	ALL	N/A					
2220	< 10 µF	≥ 10 µF					
2225	ALL	N/A					



Table 1 – Capacitance Range/Selection Waterfall (0402 – 1210 Case Sizes)

	Cap		se Si Serie			C04	02C	;		C)603	3C			C	080	5C			C1206C					C	1210	C	
Сар	Code	Vo	ltage Co	ode	9	8	4	3	9	8	4	3	5	9	8	4	3	5	9	8	4	3	5	9	8	4	3	5
	oouc	Rated	Voltage	(VDC)	6.3	10	16	25	6.3	10	16	25	50	6.3	10	16	25	50	6.3	10	16	25	50	6.3	10	16	25	50
		Capacit	ance To	lerance				Prod	uct A	vaila	bility	and	Chip '	, Thick	ness	Code	es Se	e Tab	le 2 f	or Ch	nip Th	ickn	ess D	imen	sions	;		
12,000 pF	123	J	K	М	BB	BB	BB	BB					-								-							
15,000 pF	153	J	K	М	BB	BB	BB	BB																				
18,000 pF	183	J	K	М	BB	BB	BB	BB																				
22,000 pF	223	J	K	М	BB	BB	BB	BB																				
27,000 pF	273	J	K	М	BB	BB	BB																					
33,000 pF	333	J	K	М	BB	BB	BB																					
39,000 pF	393	J	K	М	BB	BB	BB																					
47,000 pF	473	J	K	М	BB	BB	BB		CF	CF	CF	CF	CF															
56,000 pF	563	J	ĸ	М	BB	BB																						
68,000 pF	683	J	к	М	BB	BB																						
82,000 pF	823	J	K	М	BB	BB																						
0.10 µF	104	J	K	М	BB	BB			CF	CF	CF	CF																
0.12 µF	124	J	K	М					CF	CF	CF	CF																
0.15 µF	154	J	K	М					CF	CF	CF	CF		DG	DG	DG	DG	DG										
0.18 µF	184	J	K	М					CF	CF	CF			DG	DG	DG	DG	DG										
0.22 µF	224	J	K	М					CF	CF	CF			DP	DP	DP	DP	DG										
0.27 µF	274	J	к	М										DP	DP	DP	DP											
0.33 µF	334	J	к	М										DP	DP	DP	DP											
0.39 µF	394	J	к	М										DE	DE	DE	DE							FD	FD	FD	FD	FD
0.47 µF	474	J	ĸ	М										DE	DE	DE	DE		EG	EG	EG	EG	EG	FD	FD	FD	FD	FD
0.56 µF	564	J	K	М										DG	DG	DH	DH							FF	FF	FF	FF	FF
0.68 µF	684	J	K	М										DG	DG	DH	DH							FG	FG	FG	FG	FG
0.82 µF	824	J	K	М										DG	DG	DG								FL	FL	FL	FL	FL
1.0 µF	105	J	K	М										DG	DG	DG			ED	ED	ED	ED		FM	FM	FM	FM	FM
1.2 µF	125	J	K	М															EH	EH	EH	EH		FG	FG	FG	FG	
1.5 μF	155	J	K	М															EH	EH	EH	EH		FG	FG	FG	FG	
1.8 µF	185	J	ĸ	М															EF	EF	EH	EH		FG	FG	FG	FG	
2.2 µF	225	J	ĸ	М															EF	EF	EH	EH		FG	FG	FG	FG	
2.7 μF	275	J	ĸ	М															EH	EH	EH			FG	FG	FH	FH	
3.3 µF	335	J	ĸ	М															EH	EH	EH			FM	FM	FM	FM	
3.9 µF	395	J	К	М															EH	EH	EH			FG	FG	FK	FK	
4.7 μF	475	J	к	М															EH	EH	EH			FG	FG	FS	FS	
5.6 µF	565	J	К	М																				FH	FH	FH		
6.8 µF	685	J	К	М																				FM	FM	FM		
8.2 μF	825	J	K	М																				FK	FK	FK		
10 µF	106	J	K	М																				FS	FS	FS		
		Rated	Voltage	(VDC)	6.3	10	16	25	6.3	10	16	25	50	6.3	10	16	25	50	6.3	10	16	25	50	6.3	10	16	25	50
Cap	Cap Code	Vo	ltage Co	ode	9	8	4	3	9	8	4	3	5	9	8	4	3	5	9	8	4	3	5	9	8	4	3	5
		Case	e Size/S	eries		C04	02C			C	0603	C			C	0805	C			(C1206	С			C	C1210	С	



Thickness	Case	Thickness ±	Paper Q	uantity ¹	Plastic (Quantity		
Code	Size ¹	Range (mm)	7" Reel	13" Reel	7" Reel	13" Reel		
BB	0402	0.50 ± 0.05	10,000	50,000	0	0		
CF	0603	0.80 ± 0.07	4,000	15,000	0	0		
DP	0805	0.90 ± 0.10	4,000	15,000	0	0		
DE	0805	1.00 ± 0.10	0	0	2,500	10,000		
DG	0805	1.25 ± 0.15	0	0	2,500	10,000		
DH	0805	1.25 ± 0.20	0	0	2,500	10,000		
ED	1206	1.00 ± 0.10	0	0	2,500	10,000		
EF	1206	1.20 ± 0.15	0	0	2,500	10,000		
EG	1206	1.60 ± 0.15	0	0	2,000	8,000		
EH	1206	1.60 ± 0.20	0	0	2,000	8,000		
FD	1210	0.95 ± 0.10	0	0	4,000	10,000		
FF	1210	1.10 ± 0.10	0	0	2,500	10,000		
FG	1210	1.25 ± 0.15	0	0	2,500	10,000		
FL	1210	1.40 ± 0.15	0	0	2,000	8,000		
FH	1210	1.55 ± 0.15	0	0	2,000	8,000		
FM	1210	1.70 ± 0.20	0	0	2,000	8,000		
FK	1210	2.10 ± 0.20	0	0	2,000	8,000		
FS	1210	2.50 ± 0.30	0	0	1,000	4,000		
Thickness	Case	Thickness ±	7" Reel	13" Reel	7" Reel	13" Reel		
Code	Size ¹	Range (mm)	Paper Q	uantity ¹	Plastic Quantity			

Table 2A – Chip Thickness/Tape & Reel Packaging Quantities

Package quantity based on finished chip thickness specifications.

¹ If ordering using the 2 mm Tape and Reel pitch option, the packaging quantity outlined in the table above will be doubled. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".



Table 2B – Bulk Packaging Quantities

Deeker		Loose Packaging					
Раскау	ing Type	Bulk Bag (default)					
Packagin	g C-Spec ¹	N/	/A ²				
Case	Size	Packaging Quantities (pieces/unit packaging)				
EIA (in)	Metric (mm)	Minimum	Maximum				
0402	1005						
0603	1608		50,000				
0805	2012						
1206	3216						
1210	3225	1					
1808	4520						
1812	4532						
1825	4564]	20,000				
2220	5650]					
2225	5664						

¹ The "Packaging C-Spec" is a 4 to 8 digit code which identifies the packaging type and/or product grade. When ordering, the proper code must be included in the 15th through 22nd character positions of the ordering code. See "Ordering Information" section of this document for further details. Commercial Grade product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging. Contact KEMET if you require a bulk bag packaging option for Automotive Grade products.

² A packaging C-Spec (see note 1 above) is not required for "Bulk Bag" packaging (excluding Anti-Static Bulk Bag and Automotive Grade products). The 15th through 22nd character positions of the ordering code should be left blank. All product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging.



Table 3A – Land Pattern Design Recommendations per IPC-7351 – Standard Termination

EIA Size Code	Metric Size Code	Density Level A: Maximum (Most) Land Protrusion (mm)			I	Density Level B: Median (Nominal) Land Protrusion (mm)			Density Level C: Minimum (Least) Land Protrusion (mm)							
		C	Y	X	V1	V2	C	Y	X	V1	V2	C	Y	X	V1	V2
0402	1005	0.50	0.72	0.72	2.20	1.20	0.45	0.62	0.62	1.90	1.00	0.40	0.52	0.52	1.60	0.80
0603	1608	0.90	1.15	1.10	4.00	2.10	0.80	0.95	1.00	3.10	1.50	0.60	0.75	0.90	2.40	1.20
0805	2012	0.99	1.44	1.66	4.47	2.71	0.89	1.24	1.56	3.57	2.11	0.79	1.04	1.46	2.42	1.81
1206	3216	1.59	1.62	2.06	5.85	3.06	1.49	1.42	1.96	4.95	2.46	1.39	1.22	1.86	4.25	2.16
1210	3225	1.59	1.62	3.01	5.90	4.01	1.49	1.42	2.91	4.95	3.41	1.39	1.22	2.81	4.25	3.11

Density Level A: For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

Density Level B: For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC–7351).

Image below based on Density Level B for an EIA 1210 case size.







Table 3B – Land Pattern Design Recommendations per IPC-7351 – Flexible Termination

EIA Size Code	Metric Size Code	Density Level A: Maximum (Most) Land Protrusion (mm)			I	Density Level B: Median (Nominal) Land Protrusion (mm)			Density Level C: Minimum (Least) Land Protrusion (mm)							
		C	Y	X	V1	V2	C	Y	X	V1	V2	C	Y	X	V1	V2
0603	1608	0.85	1.25	1.10	4.00	2.10	0.75	1.05	1.00	3.10	1.50	0.65	0.85	0.90	2.40	1.20
0805	2012	1.00	1.35	1.55	4.40	2.60	0.90	1.15	1.45	3.50	2.00	0.75	0.95	1.35	2.80	1.70
1206	3216	1.60	1.65	1.90	5.90	2.90	1.50	1.45	1.80	5.00	2.30	1.40	1.25	1.70	4.30	2.00
1210	3225	1.60	1.65	2.80	5.90	3.80	1.50	1.45	2.70	5.00	3.20	1.40	1.25	2.60	4.30	2.90

Density Level A: For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

Density Level B: For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).

Image below based on Density Level B for an EIA 1210 case size.



Soldering Process

Recommended Soldering Technique:

- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- · All other EIA case sizes are limited to solder reflow only

Recommended Reflow Soldering Profile:

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/ J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

Profile Feature	Terminat	ion Finish
Tomereature	SnPb	100% Matte Sn
Preheat/Soak		
Temperature Minimum (T _{smin})	100°C	150°C
Temperature Maximum (T _{Smax})	150°C	200°C
Time (t_s) from T_{smin} to T_{smax}	60 – 120 seconds	60 – 120 seconds
Ramp-Up Rate (T _L to T _p)	3°C/second maximum	3°C/second maximum
Liquidous Temperature (T_L)	183°C	217°C
Time Above Liquidous (t_L)	60 – 150 seconds	60 – 150 seconds
Peak Temperature (T _P)	235°C	260°C
Time Within 5°C of Maximum Peak Temperature (t _p)	20 seconds maximum	30 seconds maximum
Ramp-Down Rate $(T_p to T_L)$	6°C/second maximum	6°C/second maximum
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum

Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.








Table 4 – Performance & Reliability: Test Methods and Conditions


Stress	Reference	Test or Inspection Method		
Terminal Strength	JIS-C-6429	Appendix 1, Note: Force of 1.8 kg for 60 seconds.		
Board Flex	JIS-C-6429	Appendix 2, Note: Standard termination system – 2.0 mm (minimum) for all except 3 mm for COG. Flexible termination system – 3.0 mm (minimum).		
		Magnification 50 X. Conditions:		
Solderability	J-STD-002	a) Method B, 4 hours at 155°C, dry heat at 235°C		
Solderability	J-31D-002	b) Method B at 215°C category 3		
		c) Method D, category 3 at 260°C		
Temperature Cycling	JESD22 Method JA-104	1,000 cycles (-55°C to +150°C). Measurement at 24 hours +/- 4 hours after test conclusion.		
Discol Llumiditu	MIL-STD-202 Method	Load Humidity: 1,000 hours 85° C/85%RH and rated voltage. Add 100K ohm resistor. Measurement at 24 hours +/- 4 hours after test conclusion.		
Biased Humidity	103	Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours +/- 4 hours after test conclusion.		
Moisture Resistance	MIL-STD-202 Method 106	t = 24 hours/cycle. Steps 7a and 7b not required. Measurement at 24 hours. +/- 4 hours after test conclusion.		
Thermal Shock	MIL-STD-202 Method 107	–55°C/+150. Note: Number of cycles required – 300. Maximum transfer time – 20 seconds. Dwell time – 15 minutes. Air – Air.		
High Temperature Life	MIL-STD-202 Method 108 /EIA-198	1,000 hours at 150°C with 2 X rated voltage applied.		
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC for 1,000 hours.		
Vibration	MIL-STD-202 Method 204	5 g's for 20 min., 12 cycles each of 3 orientations. Note: Use 8" X 5" PCB 0.031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz		
Mechanical Shock	MIL-STD-202 Method 213	Figure 1 of Method 213, Condition F.		
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.		

Storage and Handling


Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature-reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.



Construction – Standard Termination



Construction – Flexible Termination





Capacitor Marking (Optional):

These surface mount multilayer ceramic capacitors are normally supplied unmarked. If required, they can be marked as an extra cost option. Marking is available on most KEMET devices but must be requested using the correct ordering code identifier(s). If this option is requested, two sides of the ceramic body will be laser marked with a "K" to identify KEMET, followed by two characters (per EIA–198 - see table below) to identify the capacitance value. EIA 0603 case size devices are limited to the "K" character only.


Laser marking option is not available on:

- COG, Ultra Stable X8R and Y5V dielectric devices
- EIA 0402 case size devices
- EIA 0603 case size devices with Flexible Termination option.
- KPS Commercial and Automotive Grade stacked devices.

EIA Case Size	Metric Size Code	Capacitance
0603	1608	≤ 170 pF
0805	2012	≤ 150 pF
1206	3216	≤ 910 pF
1210	3225	≤ 2,000 pF
1808	4520	≤ 3,900 pF
1812	4532	≤ 6,700 pF
1825	4564	≤ 0.018 µF
2220	5650	≤ 0.027 µF
2225	5664	≤ 0.033 µF

 X7R dielectric products in capacitance values outlined below

Marking appears in legible contrast. Illustrated below is an example of an MLCC with laser marking of "KA8", which designates a KEMET device with rated capacitance of 100 μ F. Orientation of marking is vendor optional.





Capacitor Marking (Optional) cont'd

	C	apacita	ance (p	F) For \	/arious	Alpha/	Numera	al Identif	iers			
Alpha						Numera	al					
Alpha Character	9	0	1	2	3	4	5	6	7	8		
Clidiacter	Capacitance (pF)											
А	0.1	10	10	100	1,000	10,000	100,000	1,000,000	10,000,000	100,000,000		
В	0.11	1.1	11	110	1,100	11,000	110,000	1,100,000	11,000,000	110,000,000		
С	0.12	12	12	120	1,200	12,000	120,000	1,200,000	12,000,000	120,000,000		
D	0.13	13	13	130	1,300	13,000	130,000	1,300,000	13,000,000	130,000,000		
E	0.15	15	15	150	1,500	15,000	150,000	1,500,000	15,000,000	150,000,000		
F	0.16	16	16	160	1,600	16,000	160,000	1,600,000	16,000,000	160,000,000		
G	0.18	18	18	180	1,800	18,000	180,000	1,800,000	18,000,000	180,000,000		
Н	0.2	2 0	20	200	2,000	20,000	200,000	2,000,000	20,000,000	200,000,000		
J	0.22	2 2	22	220	2,200	22,000	220,000	2,200,000	22,000,000	220,000,000		
К	0.24	2.4	24	240	2,400	24,000	240,000	2,400,000	24,000,000	240,000,000		
L	0.27	2.7	27	270	2,700	27,000	270,000	2,700,000	27,000,000	270,000,000		
М	0.3	30	30	300	3,000	30,000	300,000	3,000,000	30,000,000	300,000,000		
Ν	0.33	33	33	330	3,300	33,000	330,000	3,300,000	33,000,000	330,000,000		
Р	0.36	36	36	360	3,600	36,000	360,000	3,600,000	36,000,000	360,000,000		
Q	0.39	39	39	390	3,900	39,000	390,000	3,900,000	39,000,000	390,000,000		
R	0.43	4 3	43	430	4,300	43,000	430,000	4,300,000	43,000,000	430,000,000		
S	0.47	4.7	47	470	4,700	47,000	470,000	4,700,000	47,000,000	470,000,000		
Т	0.51	5.1	51	510	5,100	51,000	510,000	5,100,000	51,000,000	510,000,000		
U	0.56	56	56	560	5,600	56,000	560,000	5,600,000	56,000,000	560,000,000		
V	0.62	6 2	62	620	6,200	62,000	620,000	6,200,000	62,000,000	620,000,000		
W	0.68	68	68	680	6,800	68,000	680,000	6,800,000	68,000,000	680,000,000		
Х	0.75	75	75	750	7,500	75,000	750,000	7,500,000	75,000,000	750,000,000		
Y	0.82	8 2	82	820	8,200	82,000	820,000	8,200,000	82,000,000	820,000,000		
Z	0.91	9.1	91	910	9,100	91,000	910,000	9,100,000	91,000,000	910,000,000		
а	0.25	2 5	25	250	2,500	25,000	250,000	2,500,000	25,000,000	250,000,000		
b	0.35	3 5	35	350	3,500	35,000	350,000	3,500,000	35,000,000	350,000,000		
d	0.4	4 0	40	400	4,000	40,000	400,000	4,000,000	40,000,000	400,000,000		
е	0.45	4 5	45	450	4,500	45,000	450,000	4,500,000	45,000,000	450,000,000		
f	0.5	5 0	50	500	5,000	50,000	500,000	5,000,000	50,000,000	500,000,000		
m	0.6	60	60	600	6,000	60,000	600,000	6,000,000	60,000,000	600,000,000		
n	0.7	7 0	70	700	7,000	70,000	700,000	7,000,000	70,000,000	700,000,000		
t	0.8	8 0	80	800	8,000	80,000	800,000	8,000,000	80,000,000	800,000,000		
у	0.9	90	90	900	9,000	90,000	900,000	9,000,000	90,000,000	900,000,000		



Tape & Reel Packaging Information

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12 and 16 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.




Table 5 – Carrier Tape Configuration, Embossed Plastic & Punched Paper (mm)

	Таре	Embosse	ed Plastic	Punche	d Paper
EIA Case Size	-	7" Reel	13" Reel	7" Reel	13" Reel
		Pitch	(P ₁)*	Pitch	(P ₁)*
01005 - 0402	8			2	2
0603	8			2/4	2/4
0805	8	4	4	4	4
1206 - 1210	8	4	4	4	4
1805 - 1808	12	4	4		
≥ 1812	12	8	8		
KPS 1210	12	8	8		
KPS 1812 & 2220	16	12	12		
Array 0508 & 0612	8	4	4		

*Refer to Figures 1 & 2 for W and P₁ carrier tape reference locations. *Refer to Tables 6 & 7 for tolerance specifications.

New 2 mm Pitch Reel Options*

Packaging Ordering Code (C-Spec)	Packaging Type/Options
C-3190	Automotive grade 7" reel unmarked
C-3191	Automotive grade 13" reel unmarked
C-7081	Commercial grade 7" reel unmarked
C-7082	Commercial grade 13" reel unmarked

* 2 mm pitch reel only available for 0603 EIA case size. 2 mm pitch reel for 0805 EIA case size under development.

Benefits of Changing from 4 mm to 2 mm Pitching Spacing

- Lower placement costs
- Double the parts on each reel results in fewer reel changes and increased efficiency
- Fewer reels result in lower packaging, shipping and storage costs, reducing waste



Figure 1 – Embossed (Plastic) Carrier Tape Dimensions




Table 6 – Embossed (Plastic) Carrier Tape Dimensions

Metric will govern

		(Constant Dim	ensions — Mil	limeters (Inc	hes)				
Tape Size	D ₀	D ₁ Minimum Note 1	E ₁	P ₀	P ₂	R Reference Note 2	S ₁ Minimum Note 3	T Maximum	T ₁ Maximum	
8 mm		1.0 (0.039)				25.0 (0.984)				
12 mm	1.5 +0.10/-0.0 (0.059 +0.004/- 0.0)	1.5	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	30	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)	
16 mm)	(0.059)				(1.181)				
	Variable Dimensions – Millimeters (Inches)									
Tape Size	Pitch	B ₁ Maximum Note 4	E ₂ Minimum	F	P ₁	T ₂ Maximum	W Maximum	A ₀ ,B ₀	& K ₀	
8 mm	Single (4 mm)	4.35 (0.171)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	2.5 (0.098)	8.3 (0.327)			
12 mm	Single (4 mm) & Double (8 mm)	8.2 (0.323)	10.25 (0.404)	5.5 ±0.05 (0.217 ±0.002)	8.0 ±0.10 (0.315 ±0.004)	4.6 (0.181)	12.3 (0.484)	Not	te 5	
16 mm	Triple (12 mm)	12.1 (0.476)	14.25 (0.561)	7.5 ±0.05 (0.138 ±0.002)	12.0 ±0.10 (0.157 ±0.004)	4.6 (0.181)	16.3 (0.642)			

1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.

2. The tape with or without components shall pass around R without damage (see Figure 6).

3. If S₁ < 1.0 mm, there may not be enough area for cover tape to be properly applied (see EIA Standard 481 paragraph 4.3 section b).

4. B, dimension is a reference dimension for tape feeder clearance only.

5. The cavity defined by A_{μ} , B_{μ} and K_{μ} shall surround the component with sufficient clearance that:

(a) the component does not protrude above the top surface of the carrier tape.

(b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.

(c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3).

(d) lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4).

(e) for KPS Series product, A_0 and B_0 are measured on a plane 0.3 mm above the bottom of the pocket.

(f) see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.



Figure 2 – Punched (Paper) Carrier Tape Dimensions




Table 7 – Punched (Paper) Carrier Tape Dimensions

Metric will govern

	Constant Dimensions – Millimeters (Inches)										
Tape Size	D ₀	E ₁	P ₀	P ₂	T ₁ Maximum	G Minimum	R Reference Note 2				
8 mm	1.5 +0.10 -0.0 (0.059 +0.004 -0.0)	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	0.10 (0.004) Maximum	0.75 (0.030)	25 (0.984)				
	Variable Dimensions – Millimeters (Inches)										
Tape Size	Pitch	E2 Minimum	F	P ₁	T Maximum	W Maximum	A ₀ B ₀				
8 mm	Half (2 mm)	6.25	3.5 ±0.05	2.0 ±0.05 (0.079 ±0.002)	1.1	8.3 (0.327)	Note 1				
8 mm	Single (4 mm)	(0.246)	(0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	(0.098)	8.3 (0.327)	NOLE I				

1. The cavity defined by $A_{ar} B_{a}$ and T shall surround the component with sufficient clearance that:

a) the component does not protrude beyond either surface of the carrier tape.

b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.

c) rotation of the component is limited to 20° maximum (see Figure 3).

d) lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4).

e) see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.

2. The tape with or without components shall pass around R without damage (see Figure 6).



Packaging Information Performance Notes

- 1. Cover Tape Break Force: 1.0 Kg minimum.
- 2. Cover Tape Peel Strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength			
8 mm	0.1 to 1.0 Newton (10 to 100 gf)			
12 and 16 mm	0.1 to 1.3 Newton (10 to 130 gf)			

The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ± 10 mm/minute.

3. Labeling: Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624*.

Figure 3 – Maximum Component Rotation




Figure 4 – Maximum Lateral Movement




Figure 5 – Bending Radius







Figure 6 – Reel Dimensions



Note: Drive spokes optional; if used, dimensions B and D shall apply.

Table 8 – Reel Dimensions

Metric will govern

	Constant Dimensions – Millimeters (Inches)										
Tape Size	А	B Minimum	С	D Minimum							
8 mm	178 ±0.20										
12 mm	(7.008 ±0.008) or	1.5 (0.059)	13.0 +0.5/-0.2 (0.521 +0.02/-0.008)	20.2 (0.795)							
16 mm	330 ±0.20 (13.000 ±0.008)		(1111)								
	Variable Dimensions – Millimeters (Inches)										
Tape Size	N Minimum	W ₁	W ₂ Maximum	W ₃							
8 mm		8.4 +1.5/-0.0 (0.331 +0.059/-0.0)	14.4 (0.567)								
12 mm	50 (1.969)	12.4 +2.0/-0.0 (0.488 +0.078/-0.0)	18.4 (0.724)	Shall accommodate tape width without interference							
16 mm		16.4 +2.0/-0.0 (0.646 +0.078/-0.0)	22.4 (0.882)								



Figure 7 – Tape Leader & Trailer Dimensions





Figure 8 – Maximum Camber





KEMET Electronic Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed.

All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

KEMET is a registered trademark of KEMET Electronics Corporation.