

## Optocoupler – Overview

Owing to the increasing degree of automation, the separation of potential between control circuits (control side / field side) is becoming increasingly significant. The connection between the controller, which is the key component of every automated system, and the various sensors and actuators must be electrically safe and free of any feedback. Optocouplers are finding increasing use here. They provide the necessary degree of safety and feature other technical properties such as:

- Low power consumption on the controller side
- High switching frequency
- No contact bounce
- Wear-free switching
- Vibration resistance
- Use independent of positioning
- No need for mechanical parts
- Long service life
- High insulation voltage

Accordingly, optocouplers are a good alternative to the traditional, mechanical relay interfaces. Modules with different input voltages and enclosure technologies are available for industrial use.

### CE marking

Weidmüller's optocouplers carry the CE mark and comply with the requirements laid down by EN 50 081 part 1 and EN 50 082 part 2. They can be used in a wide range of applications and industries.

Suitable ESD measures must be taken during installation. Overvoltage protection must be provided for long leads as protection from lightning.

# Optocoupler – Overview

## Our highlight

### MICROSERIES

#### Coupler modules in terminal format

The slot-in width of 6.1 mm allows space-saving installation of the **MICROSERIES** relays in industrial automation applications. The **MICROSERIES** is particularly suitable for the modification and extension of equipment and machinery, where it helps to make optimum use of the limited space available in switchgear cabinets.

#### Marking

The tab surfaces enable equipment to be clearly marked using a WS marker.



#### Holding and ejecting mechanism

The innovative holding and ejecting mechanism clips the assembled module securely onto the base terminal. Using the reliable eject function, the coupler can be removed quickly and simply from the base.


#### Relay and optocoupler module

Plug-in relay and optocoupler modules allow individual adjustment to function of the base module. Relay and optocouplers, are available with different power outputs, with either AgSnO and gold contacts.




#### Connection technology

Most of our relay couplers are available with screw or tension clamp connections.



#### Pluggable cross-connectors

The ZQV 4N plug-in cross-connectors are available in various colours and with different numbers of poles. They allow reliable and distinct cross-connections between the four input and output potentials.




# Optocoupler – Overview

## Control side of the optocoupler interface

### Basic structure of the optocoupler interface:


The key component is the actual optoelectronic unit (optocoupler) which is responsible for the coupling.



One important variable of this component is the current transfer rate (CTR). The CTR factor is stated as a percentage and describes the ratio between dispensed input current  $I_F$  and the maximum available output current  $I_C$ .

Example:  $I_F = 10 \text{ mA}$ ;  $\text{CTR} = 100\% \Rightarrow I_C = 10 \text{ mA}$ .

However, the CTR variable is influenced by various parameters such as ambient temperature, degree of efficiency of the luminescence diode or geometric dimensions within the component, and itself declines over time. This means that the switching thresholds change over time, partly as a result of ageing.




In order to eliminate this effect as far as possible, Weidmüller optocouplers use almost exclusively optoelectronic semiconductors with high long-term stability in terms of CTR behaviour.

The insulation strength of the component is also important, because the actual coupling of the input and output circuits results from optical transfer. This means that even in the event of a fault, the optical component will guarantee separation of both circuits. By using optoelectronic coupling elements in accordance with DIN VDE 0884, Weidmüller's optocouplers represent the ultimate in safety.

The circuitry within the module as a whole also deserves to be mentioned, with features including "protective separation" in accordance with DIN VDE 0106 part 101.

### Optocouplers for galvanic isolation or "protective separation"




The partial discharge level test as per DIN VDE 0884 is the primary prerequisite for "protective separation" with optoelectronic coupler modules. Double or reinforced insulation for "protective separation" must be partially discharge-proof. High-voltage testing, a standard procedure for relays, is not possible with semiconductors because it may actually destroy them. In the case of coupler modules with integrated optocouplers, "protective separation" for the specified rated voltage is achieved when the following requirements are satisfied:

- Testing of the optocouplers as per DIN VDE 0884
- Adherence to creepage and clearance path on circuit boards and connection elements in accordance with EN 178, DIN VDE 0106 and 0109.


A distinction is made between three basic circuits on the input side of the optocoupler interfaces:

#### Pure DC input

Here there is a reversed polarity protection diode which prevents damage to the module in the case of reversed input polarity




#### AC/DC input



Here it is not possible to reverse the polarity of the DC input signal. The disadvantage of the AC/DC input circuit

(with DC signal trigger) is the lower switching frequency of the module, because the charge capacitor ( $C_L$ , necessary for AC input signals) reduces the maximum switching frequency

#### AC input



Here again, the charging capacity has a major influence on the maximum switching frequency of the module as a whole. Weidmüller optocouplers with AC/DC or AC input signals are rated for mains frequencies of approx. 40 – 60 Hz. In the case of AC input signals, the maximum switching frequency of the optocoupler module is less than half the mains frequency. A higher switching frequency is not possible, because this would result in constant switching in the rhythm of the mains frequency.

## Load side of the optocoupler interface

Weidmüller optocoupler modules have been dimensioned and developed for use in a wide range of applications and industries.

Possible demands made on the load side of the optocoupler modules include:

- power amplification
- AC/DC and DC/AC signal conditioning
- short-circuit protection
- interference immunity


To meet these requirements, the modules are assembled with additional electronic elements which then define the overall functioning of the optocoupler module.

Accordingly, there are always two versions for the load side of the optocoupler: output as a 2-pole or 3-pole circuit.

# Optocoupler – Overview

## Optocoupler

### 2-pole DC output




The 2-pole DC output can be compared with a conventional switch. In this version it does not matter where the load is located (in the output circuit), although the necessary output supply voltage must be available with the right polarity.

Optocoupler modules are usually indicated with an output supply voltage range of, for example, 5 ... 48 Vdc. The voltage should on no account ever be lower or higher than these values. The load current should not be higher than the stated maximum output current. If current constantly exceeds this value, the output stage will be destroyed.

Derating diagrams show the relationship of output current to ambient temperature (indicated for the products on the following pages).


### 2-pole AC output



A special semiconductor module (TRIAC) is used for switching AC voltage in the output stage of the optocoupler. Here, as with the DC output, consideration must also be given to the key data such as voltage, frequency, maximum load current and ambient temperature.

Use of the zero voltage switch ensures that the load is only switched on at the zero crossover of the voltage. The modules are always equipped with suitable protection elements (varistor, RC combination) as protection from non-permissible voltage peaks.

### 3-pole DC output






In order to function reliably, this kind of output level required potential-related output supply voltage with a single output. It is rated for either positive switching (joint reference potential: GND or 0V) or negative switching (joint reference potential: positive voltage pole).

## Protection circuits

All optocoupler modules have a protection circuit in the output (usually with a freewheel diode).

The load side must be protected to prevent interference signals from coupling into other lines.




## Standards

The following standards are complied with:

- EN 50 178:  
Electronic equipment for use in high current installations
- DIN VDE 01206 part 101:  
Protection from dangerous body currents, basic requirements for "protective separation" in electrical equipment
- DIN VDE 0884:  
Optoelectronic couplers for "protective separation"
- DIN VDE 0109:  
Insulation coordination for equipment within low-voltage systems, including creepage and clearance distances for configured printed circuit boards

# Optocoupler – Overview

## Enclosure types for relay couplers




### PLUGSERIES

The modular component system represents a new generation of plug-in optocouplers. The key element is a PXS (screw clamp) or PXZ (tension clamp) innovative relay base. Both products reflect the functionality of relays or optos and Weidmüller's experience in their commercial use. PLUGSERIES is the ideal connection system between the Solid State Relay (SSR) and the application.

#### Modular principle

The new PLUGSERIES is extremely easy to handle. Commercially available SSRs are simply plugged in, retaining clips provide a firm hold, and LED displays with a recovery diode can be plugged in.

- SSRs simply plugged in: suitable for standard and TD designs
- Independent connection technology: screw or tension clamp technology, nominal cross-sectional area 0.5 ... 2.5 mm<sup>2</sup>
- Robust design of the retaining/dismantling hook
- Control voltage 24 Vac/Vdc
- Rated switching voltage 24 Vdc, 24 Vac/Vdc, 230 Vac
- Up to 5 A continuous current
- Minimum wiring workload thanks to ZQV 2.5N plug-in cross-connectors
- Modular system allows easy handling:
  - Relay base, LED display, retaining hook and SSR
  - Clips on to the TS 35
  - Marking with WS tabs on retaining hook
- Plug-in LED with recovery diode.



### MICROSERIES

Relay and optocoupler versions in the MICROSERIES are used in industrial automation applications for separating and coupling digital input and output signals. The space saving design makes them perfectly suited for use in sub-distributors or switchgear cabinets. With its compact shape, MICROSERIES combines the functions of the classical coupling level with the terminal level.

- Slot-in width 6.1 mm
- Pluggable cross-connection for four input and output potentials
- Tried and tested ZQV 4N cross-connector system
- Wide range of input voltage from 5 .. 230 V
- LED power light, reverse polarity protection diode, freewheel diode
- WEMID enclosure material (flammability VO as per UL 94)
- Innovative holding and eject mechanism
- Marking surface to take standard WS 12/6 marking

### CE marking

Weidmüller's relay couplers carry the CE mark and comply with the requirements laid down by EN 50 081 part 1 and EN 50 082 part 2. They can be used in both industrial-scale and smaller-scale applications.

Suitable ESD measures must be taken during installation. Overvoltage protection must be provided for long leads as protection from lightning.



### WAVESERIES

Innovative electronic components require a housing or enclosure which reflects their specific functions. It must allow adjusting and control functions and support technical requirements, such as heat dissipation or electromagnetic compatibility. A compact design saves space in the switchgear cabinet and reduces assembly costs. Ergonomic design is increasingly important for top-quality relay coupler interfaces.

The WAVESERIES fulfils all these criteria, with outstanding features including:

- Assembly without tools
- Printed circuit board
- Pluggable PCB
- ZQV 2.5V pluggable cross-connection
- Hinged transparent cover
- Marking with WS tabs
- Clips onto TS 35

#### Connection systems

The user can choose between BLZ screw plug-in connectors and BLZF tension clamp plug-in systems, up to 2.5 mm<sup>2</sup> and finely stranded, for the greatest possible flexibility when wiring up the circuits.

#### Printed circuit board

If the lateral locking hook is squeezed on the head end, it can be pulled out of the enclosure together with the connection level and the circuit board. The circuit board can only be pulled out without current voltage.

#### Cross-connection



The ZQV 2.5 N/2 cross-connectors can be used to connect rows of Waveseries enclosures. The cross-connection can take up to 8 A of current. It can be used for bridging the supply voltage from one electronic module to another. The voltage at the cross-connection must not exceed 50 V.

#### Ventilation slits

Diagonal ventilation slits ventilate the lower parts of the enclosures and keep temperatures moderate.

# Optocoupler – Overview

## Enclosure types for relay couplers



### DK SERIES

All components in the DKO mini-coupler are of an extremely slim design: use of advanced surface-mounted parts (SMD) allows the width to be kept to just 6 mm. The range includes 4 or 5 screw connections for conductor cross-section of 0.5 ... 4 mm<sup>2</sup>. The mini couplers offer a wide range of applications for coupling digital sensor/actuators or signals with automation devices and the process field. DKO optocouplers can be used to pick up and standardise signals from the field with different voltages.

### MCZ SERIES

The MCZ enclosure is only 6 mm wide and one of the narrowest of its kind. Its outstanding technical features include:

- Tension clamp connection to reduce assembly costs
- Integrated input/output cross-connection to reduce wiring workload

MCZO mini-conditioners (optocouplers) have 4 or 5 tension spring connections.

The cross-section of the clamping conductor is 0.5 ... 1.5 mm<sup>2</sup>.

### EG SERIES

The EG7 integral housing has a special status because it is suited only for the installation of 10 mm compact optocouplers. EG7 optocouplers can be mounted on either the TS 32 or TS 35. An RS EG7 snap-in base is also available for the OST plug-in optocouplers.



The closed EG 7 enclosures are equipped with tension clamp unit for screw connection.

Conductors with the following cross-sections can be connected:

- Integral housing EG 7: 0.5 ... 1.5 mm<sup>2</sup>
- OST clip-in base: 0.5 ... 2.5 mm<sup>2</sup>

# PLUGSERIES

Output current 24 Vdc / 2.5A



## Output

Output voltage	0 V ... 30 Vdc
Output current (max.)	2.5 A
Voltage drop at max. load	< 0.4 V
Block-state curr. (closed circuit curr.)	< 1 mA
Switch-on delay/Switch-off delay	2ms/18ms
Short-circuit proof/Protective circuit	No/integrated freewheel diode

## General data

Ambient temp., fitted w/o distance	-40 °C...+50 °C
Ambient temp., fitted w. distance	-40 °C...+50 °C
Storage temperature	-40 °C...+50 °C
Approvals	cUL, UL recognized

## Insulation coordinates (EN 50 178)

Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	2.5kV
Creepage and clearance path input - output	8mm
Overvoltage category	III
Pollution severity	2

## Dimensions

Screw connection	Tension clamp connection
Clamping range (rating- / min. / max.) mm <sup>2</sup>	2.5 / 0.5 / 2.5
Length x width x height mm	92.0 / 15.3 / 95.0

## Information

## Ordering data

### Input

Rated voltage	15 Vdc...30 Vdc
Rated current	approx. 10mA
Power rating	250 mW
Auxiliary voltage	No
Status indicator	LED green

## 24VDC/24VDC 2.5A

K

### Ordering data Complete module

Screw connection	Type	POS 24VDC/24VDC 2A		
	Order No.	<b>8610840000</b>		
Tension clamp connection	Type	POZ 24VDC/24VDC 2A		
	Order No.	<b>8610920000</b>		



### Ordering data Spare relay, pluggable

Type	SSR 24V ACDC/24 VDC 2A
Order No.	<b>8576340000</b>

### Information

# PLUGSERIES

Output current 24 Vdc / 5A



Output	
Output voltage	0 V ... 30 Vdc
Output current (max.)	5 A
Voltage drop at max. load	< 0.3 V
Block-state curr. (closed circuit curr.)	< 1 mA
Switch-on delay/Switch-off delay	2ms/18ms
Short-circuit proof/Protective circuit	No/integrated freewheel diode
General data	
Ambient temp., fitted w/o distance	-40 °C...+50 °C
Ambient temp., fitted w. distance	-40 °C...+50 °C
Storage temperature	-40 °C...+50 °C
Approvals	cUL, UL recognized
Insulation coordinates (EN 50 178)	
Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	2.5kV
Creepage and clearance path input - output	8mm
Overvoltage category	III
Pollution severity	2

Dimensions	Screw connection	Tension clamp connection
Clamping range (rating- / min. / max.) mm <sup>2</sup>	2.5 / 0.5 / 2.5	2.5 / 0.5 / 2.5
Length x width x height mm	92.0 / 15.3 / 95.0	92.0 / 15.3 / 87.0

Information

## Ordering data

### Input

Rated voltage	15 Vdc...30 Vdc
Rated current	approx. 10mA
Power rating	250 mW
Auxiliary voltage	No
Status indicator	LED green

### 24VDC/24VDC 5A




### Ordering data Complete module

Screw connection	Type	POS 24VDC/24VDC 5A		
	Order No.	<b>8610900000</b>		
Tension clamp connection	Type	POZ 24VDC/24VDC 5A		
	Order No.	<b>8610970000</b>		

### Ordering data Spare relay, pluggable



Type	SSR 24V ACDC/24 VDC 5A		
Order No.	<b>8576350000</b>		

### Information



# PLUGSERIES

Output current 24 Vuc / 1A



## Output

Output voltage	0 V ... 30 Vuc
Output current (max.)	1 A
Voltage drop at max. load	< 0.9 V
Block-state curr. (closed circuit curr.)	< 1 mA
Switch-on delay/Switch-off delay	5ms/12ms
Short-circuit proof/Protective circuit	No/integrated freewheel diode

## General data

Ambient temp., fitted w/o distance	-40 °C...+50 °C
Ambient temp., fitted w. distance	-40 °C...+50 °C
Storage temperature	-40 °C...+50 °C
Approvals	cUL, UL recognized

## Insulation coordinates (EN 50 178)

Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	4.0kV
Creepage and clearance path input - output	8mm
Overvoltage category	III
Pollution severity	2

## Dimensions

Clamping range (rating- / min. / max.)	mm <sup>2</sup>	Screw connection	Tension clamp connection
Length x width x height	mm	2.5 / 0.5 / 2.5 92.0 / 15.3 / 95.0	2.5 / 0.5 / 2.5 92.0 / 15.3 / 87.0

## Information

## Ordering data

Input	24VDC/24VUC 1A
Rated voltage	15 Vdc...30 Vdc
Rated current	approx. 10mA
Power rating	250 mW
Auxiliary voltage	No
Status indicator	LED green

K

## 24VDC/24VUC 1A

### Ordering data Complete module

Screw connection	Type	POS 24VDC/24VUC 1A
	Order No.	<b>8610890000</b>
Tension clamp connection	Type	POZ 24VDC/24VUC 1A
	Order No.	<b>8610960000</b>



### Ordering data Spare relay, pluggable

Type	SSR 24V ACDC/24VACDC
Order No.	<b>8576380000</b>

### Information

# PLUGSERIES

Output current 230 Vac / 2A



## Output

Output voltage	12 V ... 275 Vac
Output current (max.)	2 A
Voltage drop at max. load	< 1 V
Block-state curr. (closed circuit curr.)	< 1 mA
Switch-on delay/Switch-off delay	12ms/20ms
Short-circuit proof/Protective circuit	No/RC-element

## General data

Ambient temp., fitted w/o distance	-40 °C...+50 °C
Ambient temp., fitted w. distance	-40 °C...+50 °C
Storage temperature	-40 °C...+50 °C
Approvals	cUL, UL recognized

## Insulation coordinates (EN 50 178)

Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	4.0kV
Creepage and clearance path input - output	8mm
Overvoltage category	III
Pollution severity	2

## Dimensions

Screw connection	Tension clamp connection
Clamping range (rating- / min. / max.) mm <sup>2</sup>	2.5 / 0.5 / 2.5
Length x width x height mm	92.0 / 15.3 / 95.0

## Information

## Ordering data

### Input

Rated voltage	15 Vdc...30 Vdc
Rated current	approx. 10mA
Power rating	250 mW
Auxiliary voltage	No
Status indicator	LED green

## 24VDC/230VAC 2A

### Ordering data Complete module

Screw connection	Type	POS 24VDC/230VAC 2A		
	Order No.	<b>8610860000</b>		
Tension clamp connection	Type	POZ 24VDC/230VAC 2A		
	Order No.	<b>8610930000</b>		



### Ordering data Spare relay, pluggable

Type	SSR 24V ACDC/230VAC 2A	
Order No.	<b>8576370000</b>	

### Information

# PLUGSERIES

**Output current 230 Vac / 4A**



## Output

Output voltage	12 V ... 275 Vac
Output current (max.)	3 A (4 A at 20°C)
Voltage drop at max. load	< 1.1 V
Block-state curr. (closed circuit curr.)	< 1 mA
Switch-on delay/Switch-off delay	12ms/20ms
Short-circuit proof/Protective circuit	No/RC-element

## General data

Ambient temp., fitted w/o distance	-40 °C...+50 °C
Ambient temp., fitted w. distance	-40 °C...+50 °C
Storage temperature	-40 °C...+50 °C
Approvals	cUL, UL recognized

## Insulation coordinates (EN 50 178)

Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	4.0kV
Creepage and clearance path input - output	8mm
Oversupply category	III
Pollution severity	2

## Dimensions

Clamping range (rating- / min. / max.)	mm <sup>2</sup>	Screw connection	Tension clamp connection
Length x width x height	mm	2.5 / 0.5 / 2.5 92.0 / 15.3 / 95.0	2.5 / 0.5 / 2.5 92.0 / 15.3 / 87.0

## Information

### Ordering data

#### Input

Rated voltage	15 Vdc...30 Vdc
Rated current	approx. 10mA
Power rating	250 mW
Auxiliary voltage	No
Status indicator	LED green

### 24VDC/230VAC 4A

K

#### Ordering data Complete module

Screw connection	Type	POS 24VDC/230VAC 4A		
	Order No.	<b>8610910000</b>		
Tension clamp connection	Type	POZ 24VDC/230VAC 4A		
	Order No.	<b>8610980000</b>		

#### Ordering data Spare relay, pluggable

Type	SSR 24V ACDC/230VAC 4A		
Order No.	<b>8576360000</b>		


#### Information

# PLUGSERIES

## Accessories

### Schrack RP3SL

Relay for high switch-on current




## Technical data

### Empty base


Rated current	16 A
Rated voltage	250 V
Voltage strength coil / contacts	> 4 kV
Protection	IP 20
Rated cross-sectional area	2.5 mm <sup>2</sup>
Stripping length	8 mm
Ambient temperature	-40°C ... +60°C
Flammability class as per UL 94	V-0

screw connection  
tension clamp

### Tension clamp connection



### Screw connection



## Order data

### Empty base for assembly on the TS 35 mounting rail

Type	Qty	Order no.
PXS35	10	8533771001
PXZ35	10	8536691001

### Retaining clip

PRC	100	8536700000
-----	-----	------------

### LED display with freewheeling diode

6 ... 24 Vdc	PLED 24 Vdc	20	8536710000
LED red, 6 ... 24 Vdc	PLED 24 Vdc rot	20	8611010000
48 ... 60 Vdc	PLED 48 Vdc	20	8536720000
115 Vdc	PLED 115 Vdc	20	8536730000
12 ... 24 Vac	PLED 24 Vac	20	8536750000
115 Vac	PLED 120 Vac	20	8536760000
230 Vac	PLED 230 Vac	20	8536780000
LED red, 230 Vac	PLED 230 Vac rot	20	8611000000
RC combination 120...230 VAC/DC	PLRC 200 nF/200Ω	20	8566530000

### Pluggable cross-connections


2-pole	black	ZQV 2.5N/4-2SW	60	1784270000
	red	ZQV 2.5N/4-2RT	60	1784280000
	blue	ZQV 2.5N/4-2BL	60	1784290000

### Marking


10 x 5 mm	WS 10/5	200	1060860000
15 x 5 mm	WS 15/5	96	1609880000

## Operating control display

### DC version



### AC version




# MICROSERIES

## Output current 24 Vdc / 0.1A

Universal interface between control and sensor/actuator

- Pluggable cross-connection ZQV 4N
- Solid-state relay interchangeable
- Width 6.1 mm
- Screw or tension clamp connection technology
- Mounting on TS35



### 24VDC/24VDC 0.1A



### 120VUC/24VDC 0.1A



### 230VAC/24VDC 0.1A



## Technical data

### Input

Rated voltage

Rated current

Power rating

Max. input frequency

Auxiliary voltage

Status indicator

### Output

Output voltage

Output current (max.)

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay

Short-circuit proof/Protective circuit

### General data

Ambient temp., fitted w. distance

Ambient temp., fitted w/o distance

Storage temperature

Approvals

### Insulation coordinates (EN 50 178)

Standards

Rated voltage

Rated impulse voltage

Creepage and clearance path input - output

Oversupply category

Pollution severity

24 Vdc +/- 20 %

5.7mA

140 mW

No

LED green

3 V...48 Vdc

0.1 A

< 1 V

< 1 mA

35µs/355µs

No/integrated freewheel diode

-25 °C...+50 °C

-25 °C...+50 °C

-40 °C...+60 °C

CE cRUus

EN 50178

300

4.0

>= 5.5 mm

III

2

120 Vuc + 10 % / -15 %

3.4mA ac/2.8mA dc

340 mW / 0.4 VA

dc: 10 Hz / ac: 3 Hz

No

LED green

3 V...48 Vdc

0.1 A

< 1 V

< 1 mA

< 6.5 ms/< 10 ms

No/integrated freewheel diode

-25 °C...+50 °C

-25 °C...+50 °C

-40 °C...+60 °C

CE cRUus

EN 50178

300

4.0

>= 5.5 mm

III

2

230 Vac +/- 10 %

7.4mA

1.7 VA

3 Hz

No

LED green

3 V...48 Vdc

0.1 A

< 1 V

< 1 mA

< 6.5 ms/< 10 ms

No/integrated freewheel diode

-25 °C...+50 °C

-25 °C...+50 °C

-40 °C...+60 °C

CE cRUus

EN 50178

300

4.0

>= 5.5 mm

III

2

### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>  
Length x width x height mm

### Screw connection

2.50 / 0.50 / 4

93.0 x 6.1 x 92.0

### Tension clamp c.

1.50 / 0.50 / 4

93.0 x 6.1 x 92.0

### Information

CE, UL/UR

Mounting on TS35

### Screw connection

2.50 / 0.50 / 4

93.0 x 6.1 x 92.0

### Tension clamp c.

1.50 / 0.50 / 2.50

93.0 x 6.1 x 92.0

### Information

CE, UL/UR

Mounting on TS35

### Screw connection

2.50 / 0.50 / 4

93.0 x 6.1 x 92.0

### Tension clamp c.

1.50 / 0.50 / 2.50

93.0 x 6.1 x 92.0

### Information

CE, UL/UR

Mounting on TS35

## Ordering data

### Connection technology

Screw connection

Tension clamp c.

### Type

(Qty.=10)

Order No.

MOS 24Vdc / 24Vdc 0.1A

**8607340000**

MOZ 5Vdc / 24Vdc 0.1A

**8633010000**

### Type

(Qty.=10)

Order No.

MOS 120Vuc / 24Vdc 0.1A

**8607690000**

MOZ 120Vuc / 24Vdc 0.1A

**8607730000**

### Type

(Qty.=10)

Order No.

MOS 230Vac / 24Vdc 0.1A

**8607710000**

MOZ 230Vac / 24Vdc 0.1A

**8607750000**

## Accessories

### Information

Pluggable cross-connection

ZQV 4N

Pluggable cross-connection

ZQV 4N

Pluggable cross-connection

ZQV 4N

# MICROSERIES

## Output current 24 Vdc / 2A

Universal interface between control and sensor/actuator

- Pluggable cross-connection ZQV 4N
- Solid-state relay interchangeable
- Width 6.1 mm
- Screw or tension clamp connection technology
- Mounting on TS35

## 24VDC/24VDC 2A

### Technical data

#### Input

Rated voltage

Rated current

Power rating

Max. input frequency

Auxiliary voltage

Status indicator

#### Output

Output voltage

Output current (max.)

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay

Short-circuit proof/Protective circuit

#### General data

Ambient temp., fitted w. distance

Ambient temp., fitted w/o distance

Storage temperature

Approvals

#### Insulation coordinates (EN 50 178)

Standards

Rated voltage

Rated impulse voltage

Creepage and clearance path input - output

Oversupply category

Pollution severity

#### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>

Length x width x height mm

#### Information

## Ordering data

### Connection technology

Screw connection  
Tension clamp c.

### Screw connection

2.50 / 0.50 / 4

1.50 / 0.50 / 2.50

93.0 x 6.1 x 92.0

93.0 x 6.1 x 92.0

CE, UL/UR

Mounting on TS35

## 120VUC/24VDC 2A

### Technical data

#### Input

120 Vuc +/- 10 % / -15 %

3.4mA ac/2.8mA dc

340 mW / 0.4 VA

dc: 10 Hz / ac: 3 Hz

No

LED green

#### Output

3 V...33 Vdc

2 A

< 120 mV

approx. 10 µA

< 55 us/< 1.2 ms

No/integrated freewheel diode

-25 °C...+50 °C

-25 °C...+50 °C

-40 °C...+60 °C

CE cRUus

EN 50178

300

4.0

>= 5.5 mm

III

2

### Screw connection

2.50 / 0.50 / 4

1.50 / 0.50 / 2.50

93.0 x 6.1 x 92.0

93.0 x 6.1 x 92.0

CE, UL/UR

Mounting on TS35

## 230VAC/24VDC 2A

### Technical data

#### Input

230 Vac +/- 10 %

7.4mA

1.7 VA

3 Hz

No

LED green

#### Output

3 V...33 Vdc

2 A

< 120 mV

approx. 10 µA

< 6.5 ms/< 10 ms

No/integrated freewheel diode

-25 °C...+50 °C

-25 °C...+50 °C

-40 °C...+60 °C

CE cRUus

EN 50178

300

4.0

>= 5.5 mm

III

2

### Screw connection

2.50 / 0.50 / 4

1.50 / 0.50 / 2.50

93.0 x 6.1 x 92.0

93.0 x 6.1 x 92.0

CE, UL/UR

Mounting on TS35

# MICROSERIES

## Plug-in solid state relay

### SSS Relay

Switching current 100 mA

### SSS Relay

Switching current 2 A




#### Technical data


Input	Nominal control voltage
Control voltage min / max	24 Vdc
Control current at $U_{IN} = 24$ V	16 Vdc / 30 Vdc
Release voltage	7 mA $\pm 10\%$
Control circuit resistance	10 Vdc
	ca. 4 kOhm
Output	
Switching voltage	Bipolar transistor
Switching/continuous current at $U_A > 5$ Vdc	3 ... 48 Vdc
Conducting-state voltage	<b>100 mAdc</b>
	< 1 Vdc
Insulation	
Test voltage between control circuit / switching circuit	2.5 kV
Other data	
Operation temperature range	-20°C ... +60°C
Storage temperature range	-40°C ... +70°C
Weight	3.65 g
Approvals	cUL us
* Ambient temperature 20°C	
Main-line wiring diagram	

For other data see also <http://em.tycoelectronics.com>

24 Vdc	60 Vdc
18 Vdc / 30 Vdc	52 Vdc / 72 Vdc
7 mA $\pm 10\%$	2.8 mA $\pm 10\%$
10 Vdc	40 Vdc
ca. 4 kOhm	ca. 20 kOhm
Output	
Switching voltage	Bipolar transistor
Switching/continuous current at $U_A > 5$ Vdc	3 ... 48 Vdc
Conducting-state voltage	<b>100 mAdc</b>
	< 1 Vdc
Insulation	
Test voltage between control circuit / switching circuit	2.5 kV
Other data	
Operation temperature range	-20°C ... +60°C
Storage temperature range	-40°C ... +70°C
Weight	3.65 g
Approvals	cUL us
* Ambient temperature 20°C	
Main-line wiring diagram	



24 Vdc	60 Vdc
18 Vdc / 30 Vdc	35 Vdc / 72 Vdc
7 mA $\pm 10\%$	3.0 mA $\pm 10\%$
10 Vdc	20 Vdc
ca. 3.2 kOhm	ca. 16 kOhm
Output	
Switching voltage	MOS-FET
Switching/continuous current at $U_A > 5$ Vdc	3 ... 33 Vdc
Conducting-state voltage	<b>2 Adc</b>
	< 120 mVdc
Insulation	
Test voltage between control circuit / switching circuit	2.5 kV
Other data	
Operation temperature range	-20°C ... +60°C
Storage temperature range	-40°C ... +70°C
Weight	3.65 g
Approvals	cUL us
* Ambient temperature 20°C	
Main-line wiring diagram	



#### Order data



Nominal control voltage	24 Vdc 60 Vdc

Type	Order no.
SSS Relay 24 V / 24 V 0.1 Adc	4061180000
SSS Relay 60 V / 24 V 0.1 Adc	4061230000

Type	Order no.
SSS Relay 24 V / 24 V 2 Adc	4061190000
SSS Relay 60 V / 24 V 2 Adc	4061200000

#### Dimensional drawings

Print picture



# MICROSERIES

## Accessories

## General data – MICROSERIES

### Pluggable cross-connection

Type	No. of poles	Qty	Order no.
<b>Yellow</b>			
ZQV 4N / 2 GE	2	60	<b>1758250000</b>
ZQV 4N / 3 GE	3	60	<b>1762630000</b>
ZQV 4N / 4 GE	4	60	<b>1762620000</b>
ZQV 4N / 10 GE	10	20	<b>1758260000</b>
ZQV 4N / 41 GE	41	10	<b>1758270000</b>
<b>Red</b>			
ZQV 4N / 2 RT	2	60	<b>1793950000</b>
ZQV 4N / 3 RT	3	60	<b>1793980000</b>
ZQV 4N / 4 RT	4	60	<b>1794010000</b>
ZQV 4N / 10 RT	10	20	<b>1794040000</b>
ZQV 4N / 41 RT	41	10	<b>1794070000</b>
<b>Blue</b>			
ZQV 4N / 2 BL	2	60	<b>1793960000</b>
ZQV 4N / 3 BL	3	60	<b>1793990000</b>
ZQV 4N / 4 BL	4	60	<b>1794020000</b>
ZQV 4N / 10 BL	10	20	<b>1794050000</b>
ZQV 4N / 41 BL	41	10	<b>1794080000</b>
<b>Black</b>			
ZQV 4N / 2 SW	2	60	<b>1793970000</b>
ZQV 4N / 3 SW	3	60	<b>1794000000</b>
ZQV 4N / 4 SW	4	60	<b>1794030000</b>
ZQV 4N / 10 SW	10	20	<b>1794060000</b>
ZQV 4N / 41 SW	41	10	<b>1794090000</b>


### Other accessories

Type	Qty	Order no.
<b>Marker</b>		
WS 12/6	12 x 6 mm	200 <b>1061160000</b>
<b>Labels, laser mark</b>		
LM MT 300 15/6 ge	484 labels/Bogen	10 <b>1686360000</b>
<b>Screwdriver</b>		
SD 0.6 x 3.5 x 100	10	<b>9008330000</b>

### Technical data


	Tension clamp connection	Screw connection
<b>Clamping conductor</b>		
Solid H07V-U	mm <sup>2</sup>	0.5 ... 2.5
Flexible H07V-K	mm <sup>2</sup>	0.5 ... 2.5
"f" with wire end ferrule as per DIN 46 228 / 1	mm <sup>2</sup>	0.5 ... 1.5
"f" with wire end ferrule with plastic collar	mm <sup>2</sup>	0.5 ... 1.5
Max. clamping range	mm <sup>2</sup>	0.13 ... 2.5
Plug gauge as per IEC 60 947-1	size	A 2
		A 3
<b>General technical data</b>		
Rated torque	-	0.6
Constant current of the cross-connection 2-pole	A	10
Constant current of the cross-connection multi-pole	A	10
Stripping length	mm	10
Protection	IP 20	IP 20
Enclosure material	Wemid	Wemid
Flammability class as per UL 94	V-0	V-0
Rated current	A	6
Rated voltage	V	250

### Dimensioned drawing



# WAVESERIES

**Output voltage 24 Vdc, negative switching,  
wide input range**



## Output

Output voltage 18 Vdc...24 Vdc...30 Vdc

Output current (max.) 2A, negative switching

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay 1 ms/6 ms

Short-circuit proof/Protective circuit

No/varistor

## General data

Ambient temp., fitted w/o distance -25 °C...+50 °C

Ambient temp., fitted w. distance -25 °C...+50 °C

Storage temperature -40 °C...+85 °C

Approvals UL/CSA

## Insulation coordinates (EN 50 178)

Standards EN 50178

Rated voltage 300V

Rated impulse voltage 6.0kV

Creepage and clearance path input - output => 5.5 mm

Overvoltage category III

Pollution severity 2

## Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup> 1.5 / 0.5 / 2.5

Length x width x height mm 72.0 / 22.5 / 92.4

## Ordering data

### Input

Rated voltage	4.0 Vdc...5 Vdc...6.0 Vdc
Rated current	7.5...19mA
Power rating	30 ...114 mW
Auxiliary voltage	No
Status indicator	LED green in input

### 5VDC

K

## Ordering data Complete module

Screw connection	Type	WOS 1 5VDC		
	Order No.	<b>8275430000</b>		

## Tension clamp connection

Type				
Order No.				

## Ordering data Spare relay, pluggable

Type				
Order No.				

## Information


# WAVESERIES

Output voltage 5-48 Vdc



--

<b>Output</b>		
Output voltage	5 Vdc...48 Vdc	
Output current (max.)	100 mA	
Voltage drop at max. load		
Block-state curr. (closed circuit curr.)		
Switch-on delay/Switch-off delay	8 ms/35 ms	
Short-circuit proof/Protective circuit	No/varistor, integral freewheeling diode	
<b>General data</b>		
Ambient temp., fitted w/o distance	-25 °C...+60 °C	
Ambient temp., fitted w. distance	-25 °C...+60 °C	
Storage temperature	-40 °C...+85 °C	
Approvals	UL/CSA	
<b>Insulation coordinates (EN 50 178)</b>		
Standards	EN 50178	
Rated voltage	300V	
Rated impulse voltage	6.0kV	
Creepage and clearance path input - output	=> 5.5 mm	
Overvoltage category	III	
Pollution severity	2	
<b>Dimensions</b>		
Clamping range (rating- / min. / max.)	mm <sup>2</sup>	1.5 / 0.5 / 2.5
Length x width x height	mm	72.0 / 22.5 / 92.4
<b>Information</b>		

## Ordering data

### Input

Rated voltage	3.5 Vdc...15 Vdc
Rated current	10...25mA
Power rating	32 ... 375 mW
Auxiliary voltage	No
Status indicator	LED green in input

### 3.5-15VDC 5KHZ

## Ordering data Complete module

Screw connection	Type	WOS1 3.5-15VDC 5KHZ		
	Order No.	<b>8275390000</b>		

## Tension clamp connection

Type				
Order No.				


## Ordering data Spare relay, pluggable

Type				
Order No.				

## Information


# WAVESERIES

**Output voltage 24 Vdc, 0.5 A,  
short-circuit proof**



<b>Output</b>	
Output voltage	12 Vdc...24 Vdc...28 Vdc
Output current (max.)	500 mA
Voltage drop at max. load	
Block-state curr. (closed circuit curr.)	
Switch-on delay/Switch-off delay	approx. 10 ms/approx. 20 ms
Short-circuit proof/Protective circuit	Yes/ max. 96 h/varistor, polarity reversal protection
<b>General data</b>	
Ambient temp., fitted w/o distance	-25 °C...+60 °C
Ambient temp., fitted w. distance	-25 °C...+60 °C
Storage temperature	-40 °C...+85 °C
Approvals	UL/CSA
<b>Insulation coordinates (EN 50 178)</b>	
Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	6.0kV
Creepage and clearance path input - output	=> 5.5 mm
Oversupply category	III
Pollution severity	2
<b>Dimensions</b>	
Clamping range (rating- / min. / max.)	mm <sup>2</sup>
Length x width x height	1.5 / 0.5 / 2.5
	72.0 / 22.5 / 92.4
<b>Information</b>	

## Ordering data

### Input

Rated voltage	10 Vdc...12 Vdc...14 Vdc
Rated current	15mA ac/12mA dc
Power rating	0.18 VA / 0.14 W
Auxiliary voltage	No
Status indicator	LED green in output

### 12VUC/24VDC 0.5A

### 15-60VDC 1KHZ

### 115VUC/24VDC 0.5A

### 230VUC/24VDC 0.5A

15 Vdc...60 Vdc
1.4...4.1mA
21 ... 246 mW
No
LED green in output

115 Vuc, max. 130 Vuc
2.9mA ac/3.1mA dc
0.16 VA / 0.23 W
No
LED green in output

230 Vuc, max. 250 Vuc
11.5mA ac/1.8mA dc
2.6 VA / 0.4 W
No
LED green in output

### Ordering data Complete module

Screw connection	Type	WOS1 12VUC	WOS1 15-60VDC 1KHZ	WOS1 115VUC	WOS1 230VUC
Order No.		<b>8275500000</b>	<b>8237730000</b>	<b>8235180000</b>	<b>8275380000</b>

### Tension clamp connection

Order No.	


### Ordering data Spare relay, pluggable

Type	
Order No.	

### Information


# WAVESERIES

**Output voltage 24 Vdc, 5 A,  
short-circuit proof**



<b>Output</b>	
Output voltage	19.2 Vdc...24 Vdc...28.8 Vdc
Output current (max.)	5 A
Voltage drop at max. load	
Block-state curr. (closed circuit curr.)	
Switch-on delay/Switch-off delay	approx. 8 ms/25 ms
Short-circuit proof/Protective circuit	Yes/ max. 96 h/varistor, polarity reversal protection
<b>General data</b>	
Ambient temp., fitted w/o distance	-25 °C...+50 °C
Ambient temp., fitted w. distance	-25 °C...+50 °C
Storage temperature	-40 °C...+85 °C
Approvals	UL/CSA
<b>Insulation coordinates (EN 50 178)</b>	
Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	6.0kV
Creepage and clearance path input - output	=> 5.5 mm
Oversupply category	III
Pollution severity	2
<b>Dimensions</b>	
Clamping range (rating- / min. / max.)	mm <sup>2</sup>
Length x width x height	mm
<b>Information</b>	

## Ordering data

### Input

Rated voltage	24 Vuc +/- 10 %
Rated current	16.3mA ac/13.5mA dc
Power rating	0.39 VA / 0.32 W
Auxiliary voltage	No
Status indicator	LED green in output

## 24VUC/24VDC 5A

## 115VUC/24VDC 5A

## 230VUC/24VDC 5A

K

### Ordering data Complete module

Screw connection	Type	WOS2 24VUC	WOS2 115VUC	WOS2 230VUC
	Order No.	<b>8275190000</b>	<b>8296250000</b>	<b>8275220000</b>

### Tension clamp connection

Type	
Order No.	

Order No.

### Ordering data Spare relay, pluggable


Type	
Order No.	

Order No.

### Information


# WAVESERIES

**Output voltage 230 Vac, 3.5 A**



<b>Output</b>	
Output voltage	24 Vac...250 Vac
Output current (max.)	3.5 A
Voltage drop at max. load	
Block-state curr. (closed circuit curr.)	
Switch-on delay/Switch-off delay	max. 20 ms/max. 20 ms
Short-circuit proof/Protective circuit	No/RC-combination with resistor
<b>General data</b>	
Ambient temp., fitted w/o distance	-25 °C...+50 °C
Ambient temp., fitted w. distance	-25 °C...+50 °C
Storage temperature	-40 °C...+85 °C
Approvals	UL/CSA
<b>Insulation coordinates (EN 50 178)</b>	
Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	6.0kV
Creepage and clearance path input - output	=> 5.5 mm
Overvoltage category	III
Pollution severity	2
<b>Dimensions</b>	
Clamping range (rating- / min. / max.)	mm <sup>2</sup>
Length x width x height	1.5 / 0.5 / 2.5 92.4 / 22.5 / 112.4
<b>Information</b>	

## Ordering data

### Input

Rated voltage	15 Vuc...60 Vac/ 66 Vdc
Rated current	3.3...5.3mA ac/3.8...5.6mA dc
Power rating	0.31 VA / 0.33 W
Auxiliary voltage	No
Status indicator	LED green in input

### 15-60VUC/24VDC 5A

### 115VUC/230VAC 3.5A

### 230VUC/230VAC 3.5A

## K

### Ordering data Complete module

Screw connection	Type	WOS2 15-60VAC 66VDC	WOS2 115VUC	WOS2 230VUC
	Order No.	<b>8275440000</b>	<b>8259950000</b>	<b>8275400000</b>

### Tension clamp connection

Type	
Order No.	


### Ordering data Spare relay, pluggable

Type	
Order No.	

### Information


# WAVESERIES

**Output volt. 24 Vdc, 0.5 A,  
short-circuit proof, 4 channels**



<b>Output</b>	
Output voltage	12 Vdc...24 Vdc...28 Vdc
Output current (max.)	0.5 A per channel
Voltage drop at max. load	
Block-state curr. (closed circuit curr.)	
Switch-on delay/Switch-off delay	<20 ms/<50 ms
Short-circuit proof/Protective circuit	Yes/varistor, polarity reversal protection
<b>General data</b>	
Ambient temp., fitted w/o distance	-25 °C...+50 °C
Ambient temp., fitted w. distance	-25 °C...+50 °C
Storage temperature	-40 °C...+85 °C
Approvals	UL/CSA
<b>Insulation coordinates (EN 50 178)</b>	
Standards	EN 50178
Rated voltage	150V
Rated impulse voltage	6.0kV
Creepage and clearance path input - output	=> 3 mm
Oversupply category	III
Pollution severity	2
<b>Dimensions</b>	
Clamping range (rating- / min. / max.)	mm <sup>2</sup>
Length x width x height	92.4 / 22.5 / 112.4
<b>Information</b>	

## Ordering data

### Input

Rated voltage	18 Vuc...30 Vuc
Rated current	2.8mA ac/3.7mA dc
Power rating	0.4 VA / 0.3 W
Auxiliary voltage	No
Status indicator	LED green in output

### 24VUC/24VDC 0.5A

### 115VUC/24VDC 0.5A

### 230VUC/24VDC 0.5A

K

### Ordering data Complete module

Screw connection	Type	WOS2 24VUC 4C	WOS2 115VUC 4C	WOS2 230VUC 4C
	Order No.	<b>8237720000</b>	<b>8275360000</b>	<b>8275340000</b>

### Tension clamp connection

Type				
Order No.				


### Ordering data Spare relay, pluggable

Type				
Order No.				

### Information


# WAVESERIES

For high switching frequency up to 100kHz



<b>Output</b>	
Output voltage	21.6 Vdc...24 Vdc...26.4 Vdc
Output current (max.)	50 mA
Voltage drop at max. load	
Block-state curr. (closed circuit curr.)	
Switch-on delay/Switch-off delay	1 µs/7 µs
Short-circuit proof/Protective circuit	No/varistor, polarity reversal protection
<b>General data</b>	
Ambient temp., fitted w/o distance	-25 °C...+60 °C
Ambient temp., fitted w. distance	-25 °C...+60 °C
Storage temperature	-40 °C...+85 °C
Approvals	UL/CSA
<b>Insulation coordinates (EN 50 178)</b>	
Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	6.0kV
Creepage and clearance path input - output	=> 5.5 mm
Overvoltage category	III
Pollution severity	2
<b>Dimensions</b>	
Clamping range (rating- / min. / max.)	mm <sup>2</sup>
Length x width x height	mm
<b>Information</b>	

## Ordering data

<b>Input</b>	
Rated voltage	5 V TTL
Rated current	13mA
Power rating	65 mW
Auxiliary voltage	5 V
Status indicator	LED green in input

## 5VTTL 50KHZ

## 12-28VDC 100KHZ

<b>Ordering data Complete module</b>				
Screw connection	Type	WOS1 5VTTL 50KHZ	WOS1 12-28VDC 100KHZ	
Order No.		<b>8275210000</b>	<b>8275450000</b>	
<b>Tension clamp connection</b>				
Type				
Order No.				
<b>Ordering data Spare relay, pluggable</b>				
Type				
Order No.				
<b>Information</b>				

# MCZ-SERIES

## MiniConditioner MCZ O



Universal interface between control and sensor/actuator

Direct switching of load currents upto 2Adc



MCZ O with following features:

- Tension clamp connection technology
- Pluggable cross-connection
- Width 6mm

## 24 VUC



## 24VUC/24V 2A



## Technical data

### Input

Rated voltage

Rated current

Power rating

Max. input frequency

Auxiliary voltage

Status indicator

### Output

Output voltage

Output current (max.)

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay

Short-circuit proof/Protective circuit

### General data

Ambient temp., fitted w. distance

Ambient temp., fitted w/o distance

Storage temperature

Approvals

### Insulation coordinates (EN 50 178)

Standards

Rated voltage

Rated impulse voltage

Creepage and clearance path input - output

Oversupply category

Pollution severity

24 Vuc +/- 20 %

11mA ac/9mA dc

230mW / 280mVA

dc: 10 Hz/ac: 5 Hz

No

LED green

5...48Vdc

20 mA

< = 1 V

dc 20 ms/ ac 10 ms//ac 45ms/dc 40ms

No/integrated freewheel diode

-25 °C...+50 °C

-25 °C...+50 °C

-40 °C...+85 °C

CE, UL, CSA

EN 50178

300V

6.0kV

>= 5.5 mm

III

2

24 Vuc +/- 20 %

13mA ac/12mA dc

195mW / 220mVA

dc: 30 Hz/ac: 10 Hz

No

LED green

24 Vdc +- 20%

2 A

/

No/varistor

-25 °C...+40 °C

-25 °C...+40 °C

-40 °C...+60 °C

CE, UL, CSA

EN 50178

300V

6.0kV

>= 5.5 mm

III

2

### Dimensions

Clamping range (rating- / min. / max.)

mm<sup>2</sup>

Length x width x height

mm

### Tension clamp c.

1.50 / 0.50 / 1.50

91.0 x 6.0 x 64.0

### Tension clamp c.

1.50 / 0.50 / 1.50

91.0 x 6.0 x 64.0

### Information

CE, UL, CSA

Mounting on TS35

CE, UL, CSA

Mounting on TS35

## Ordering data

### Connection technology

Tension clamp c.

Type Qty. Order No.

MCZ O 24VUC 10 8365940000

Type Qty. Order No.

MCZ O 24VUC 10 8287730000

### Information

End plate

AP MCZ1.5 8389030000

End plate

AP MCZ 8389030000

## Accessories

### Information

# MCZ-SERIES


## MiniConditioner MCZ O

Universal interface between control and sensor/actuator




MCZ O with following features:

- Tension clamp connection technology
- Pluggable cross-connection
- Width 6mm

### 120VUC



### 230VAC



## Technical data

### Input

Rated voltage

120 Vuc +5/-15 %

Rated current

3mA

Power rating

350mW / 400mVA

Max. input frequency

Ac: 5 Hz duty factor 1:2, dc: 20 Hz duty factor 1:2

Auxiliary voltage

No

Status indicator

LED green

### Output

Output voltage

5...48 Vdc

Output current (max.)

50 mA

Voltage drop at max. load

< 1.6 V

Block-state curr. (closed circuit curr.)

0.16 mA

Switch-on delay/Switch-off delay

<= 30 ms /<= 40 ms

Short-circuit proof/Protective circuit

No/integrated freewheel diode

### General data

Ambient temp., fitted w. distance

-25 °C...+50 °C

Ambient temp., fitted w/o distance

-25 °C...+40 °C

Storage temperature

-40 °C...+60 °C

Approvals

CE, UL, CSA

### Insulation coordinates (EN 50 178)

Standards

EN 50178

Rated voltage

300V

Rated impulse voltage

6.0kV

Creepage and clearance path input - output

>= 5.5 mm

Oversupply category

III

Pollution severity

2

### Dimensions

Clamping range (rating- / min. / max.)

mm<sup>2</sup>

Length x width x height

mm

### Tension clamp c.

1.50 / 0.50 / 1.50

91.0 x 6.0 x 64.0

### Tension clamp c.

1.50 / 0.50 / 1.50

91.0 x 6.0 x 64.0

### Information

CE, UL, CSA

Mounting on TS35

CE, UL, CSA

Mounting on TS35

## Ordering data

### Connection technology

Tension clamp c.

### Type

MCZ O 120VUC

### Qty.

10

### Order No.

8421060000

### Type

MCZ O 230VAC

### Qty.

10

### Order No.

8421380000

### Information

End plate

AP MCZ 8389030000

End plate

AP MCZ 8389030000

## Accessories



### Information

# MCZ-SERIES



## MiniConditioner MCZ O

- Module can be used as an universal interface:
- Between control and actuator, to convert signals from 24 Vdc to 5 VTTL
  - Between control and actuator, to convert signals from 5 VTTL to 5...48 Vdc

## 24VDC/5VTTL



## 5VTTL/5...48 VDC



## Technical data

### Input

Rated voltage  
Rated current  
Power rating  
Max. input frequency  
Auxiliary voltage  
Status indicator

24 Vdc +/- 16 %  
4.7mA  
112 mW  
100 kHz duty factor 1:2, 50 kHz duty factor 1:10  
No  
LED green

5 V TTL  
1µA  
10 mW  
2.4 kHz  
5 V  
LED green

### Output

Output voltage  
Output current (max.)  
Voltage drop at max. load  
Block-state curr. (closed circuit curr.)  
Switch-on delay/Switch-off delay  
Short-circuit proof/Protective circuit

5 V TTL(4.75...5.25 V)  
8 mA, fan out = 20 LS-TTL  
  
1 µs (at 20 Vdc)/2.5 µs (at 28 Vdc)  
/diode

5...48Vdc  
100 mA  
<=1.8  
  
/  
/diode

### General data

Ambient temp., fitted w. distance  
Ambient temp., fitted w/o distance  
Storage temperature  
Approvals

-25 °C...+50 °C  
-25 °C...+40 °C  
-40 °C...+60 °C  
CE, UL, CSA

-25 °C...+50 °C  
-25 °C...+50 °C  
-40 °C...+85 °C  
CE, UL, CSA

### Insulation coordinates (EN 50 178)

Standards  
Rated voltage  
Rated impulse voltage  
Creepage and clearance path input - output  
Overvoltage category  
Pollution severity

EN 50178  
300V  
6.0kV  
>= 5.5 mm  
III  
2

EN 50178  
300V  
6.0kV  
>= 5.5 mm  
III  
2

K

### Dimensions

Clamping range (rating- / min. / max.)  
Length x width x height

### Tension clamp c.

1.50 / 0.50 / 1.50  
91.0 x 6.0 x 64.0

### Tension clamp c.

1.50 / 0.50 / 1.50  
91.0 x 6.0 x 64.0

### Information

CE, UL, CSA  
Mounting on TS35

CE, UL, CSA  
Mounting on TS35

## Ordering data

### Connection technology

Tension clamp c.

Type Qty. Order No.  
MCZ O 24VDC 10 8324610000

Type Qty. Order No.  
MCZ O 5VTTL 10 8398940000

### Information

End plate  
AP MCZ 8389030000

End plate  
AP MCZ 8389030000

## Accessories

### Information

# DK-SERIES


## Minicoupler DKO

- Coupling of digital sensor-/actuator signals between PLC and process
- Low-cost solution for adaption of level and potential
- Low input power
- Screw connection technology
- 6 mm width
- Mounting on TS35




### 5VDC



### 5VTTL



### 12VDC 10 KHZ



## Technical data

### Input

Rated voltage	5 Vdc +/- 5 %
Rated current	10 mA
Power rating	50 mW
Max. input frequency	20 Hz
Auxiliary voltage	No
Status indicator	LED green

### Output

Output voltage	5...48 Vdc
Output current (max.)	20 mA
Voltage drop at max. load	< 1.6 V
Block-state curr. (closed circuit curr.)	50 µA
Switch-on delay/Switch-off delay	<= 15 µs / <= 70 µs
Short-circuit proof/Protective circuit	No/diode

### General data

Ambient temp., fitted w. distance	-25 °C...+50 °C
Ambient temp., fitted w/o distance	-25 °C...+40 °C
Storage temperature	-40 °C...+85 °C
Approvals	CE

### Insulation coordinates (EN 50 178)

Standards	EN 50178
Rated voltage	150V
Rated impulse voltage	4.0kV
Creepage and clearance path input - output	>= 4 mm
Overshoot category	IV
Pollution severity	2

K

### Dimensions

Clamping range (rating- / min. / max.)	mm <sup>2</sup>
Length x width x height	mm

### Information

# DK-SERIES


## Minicoupler DKO

- Coupling of digital sensor-/actuator signals between PLC and process
- Low-cost solution for adaption of level and potential
- Low input power
- Screw connection technology
- 6 mm width
- Mounting on TS35

### 24VUC



### 24VDC 3KHZ



### 24VDC 3KHZ



## Technical data

### Input

Rated voltage

Rated current

Power rating

Max. input frequency

Auxiliary voltage

Status indicator

### Output

Output voltage

Output current (max.)

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay

Short-circuit proof/Protective circuit

### General data

Ambient temp., fitted w. distance

Ambient temp., fitted w/o distance

Storage temperature

Approvals

### Insulation coordinates (EN 50 178)

Standards

Rated voltage

Rated impulse voltage

Creepage and clearance path input - output

Oversupply category

Pollution severity

### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>

Length x width x height mm

### Information

24 Vuc +/- 10 %

11.4 mA ac / 9.6 mA dc

280 mVA / 230 mW

10 Hz at dc

No

LED green

5...48 Vdc

20 mA

< = 1 V

< = 50 µA

< = 15 ms at dc / < = 25 ms at dc

No/diode

-25 °C...+50 °C

-25 °C...+40 °C

-40 °C...+85 °C

CE

EN 50178

300V

4.0kV

> = 4 mm

III

2

24 Vdc +/- 10 %

< = 15 mA

max. 360 mW

3 kHz

No

LED green

5...48 Vdc

20 mA

< = 900 mV

0.16 mA

approx. 50 µs/approx. 80 µs

No/diode

-25 °C...+50 °C

-25 °C...+40 °C

-40 °C...+85 °C

CE

EN 50178

300V

4.0kV

> = 4 mm

III

2

24 Vdc +/- 10 %

< = 15 mA

max. 360 mW

3 kHz

No

LED green

5...48 Vdc

20 mA

< = 900 mV

50 µA

approx. 50 µs/approx. 80 µs

No/diode

-25 °C...+50 °C

-25 °C...+40 °C

-40 °C...+85 °C

CE

EN 50178

300V

4.0kV

> = 4 mm

III

2

### Ordering data

#### Connection technology

Screw connection

#### Screw connection

4 / 0.50 / 4

65.0 x 6.0 x 57.0

#### Screw connection

4 / 0.50 / 4

65.0 x 6.0 x 57.0

#### Screw connection

4 / 0.50 / 4

65.0 x 6.0 x 57.0

#### Type (Qty.=10)

#### Order No.

DKO 35 24VUC

**8008150000**

DKO 35 24VDC 3KHZ E:U

**8028300000**

DKO 35 24VDC 3KHZ E:O

**8215640000**

### Information

Input bottom

Input bottom

Input top

### Accessories

#### Information

End plate

AP DK4 0687560000

End plate

AP DK4 0687560000

End plate


AP DK4 0687560000

# DK-SERIES


## Minicoupler DKO

- Coupling of digital sensor-/actuator signals between PLC and process
- Low-cost solution for adaption of level and potential
- Low input power
- Screw connection technology
- 6 mm width
- Mounting on TS35


### 24VDC 3KHZ



### 24VDC 100Hz



### 24VDC 100Hz



## Technical data

### Input

Rated voltage

24 Vdc +/- 10 %

Rated current

8.5 mA

Power rating

max. 204 mW

Max. input frequency

3 kHz

Auxiliary voltage

No

Status indicator

LED green

### Output

Output voltage

5...48 Vdc

Output current (max.)

20 mA

Voltage drop at max. load

&lt; = 900 mV

Block-state curr. (closed circuit curr.)

50 µA

Switch-on delay/Switch-off delay

approx. 50 µs/approx. 80 µs

Short-circuit proof/Protective circuit

No/diode

### General data

Ambient temp., fitted w. distance

-25 °C...+50 °C

Ambient temp., fitted w/o distance

-25 °C...+40 °C

Storage temperature

-40 °C...+85 °C

Approvals

CE

### Insulation coordinates (EN 50 178)

Standards

EN 50178

Rated voltage

EN 50178

Rated impulse voltage

300V

Creepage and clearance path input - output

4.0kV

Overvoltage category

&gt;= 4 mm

Pollution severity

III


2

# DK-SERIES


## Minicoupler DKO

- Coupling of digital sensor-/actuator signals between PLC and process
- Low-cost solution for adaption of level and potential
- Low input power
- Screw connection technology
- 6 mm width
- Mounting on TS35





### 24VDC 200Hz



### 24VDC 200Hz



### 24VDC 50KHZ



## Technical data

### Input

Rated voltage

Rated current

Power rating

Max. input frequency

Auxiliary voltage

Status indicator

### Output

Output voltage

Output current (max.)

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay

Short-circuit proof/Protective circuit

### General data

Ambient temp., fitted w. distance

Ambient temp., fitted w/o distance

Storage temperature

Approvals

### Insulation coordinates (EN 50 178)

Standards

Rated voltage

Rated impulse voltage

Creepage and clearance path input - output

Oversupply category

Pollution severity

### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>  
Length x width x height mm

### Information

### Ordering data

#### Connection technology

Screw connection

### Screw connection

4 / 0.50 / 4  
65.0 x 6.0 x 57.0

### Screw connection

4 / 0.50 / 4  
65.0 x 6.0 x 57.0

### Screw connection

4 / 0.50 / 4  
77.0 x 6.0 x 62.0

### Accessories

#### Information

#### Type (Qty.=10) Order No.

DKO 35 24VDC E:U 8019590000

#### Type (Qty.=10) Order No.

DKO 35 24VDC E:O 8215630000

#### Type (Qty.=10) Order No.


DKO DK5 24VDC 50KHZ 8228640000

# DK-SERIES

## Minicoupler DKO

- Coupling of digital sensor-/actuator signals between PLC and process
- Low-cost solution for adaption of level and potential
- Low input power
- Screw connection technology
- 6 mm width
- Mounting on TS35

## 24VUC



## 115VUC



## 230VUC



## Technical data

### Input

Rated voltage

Rated current

Power rating

Max. input frequency

Auxiliary voltage

Status indicator

### Output

Output voltage

Output current (max.)

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay

Short-circuit proof/Protective circuit

### General data

Ambient temp., fitted w. distance

Ambient temp., fitted w/o distance

Storage temperature

Approvals

### Insulation coordinates (EN 50 178)

Standards

Rated voltage

Rated impulse voltage

Creepage and clearance path input - output

Overvoltage category

Pollution severity

24 Vuc +/- 20 %

13 mA ac / 12 mA dc

max.: 220 mVA / 195 mW

&lt;e; 10 Hz

No

LED green

24 Vdc +/- 20%

2 A

2 ms/7 ms

No/

-25 °C...+50 °C

-25 °C...+40 °C

-40 °C...+85 °C

CE

EN 50178

300V

6.0kV

&gt;= 5.5 mm

IV

2

115 Vuc +5 %/-15 %

2.65 mA ac / 3 mA dc

390 mVA / 350 mW

20Hz dc, 5Hz ac

No

LED green

5...48 Vdc

50 mA

&lt; 1.6 V

0.16 mA

17.4 ms/27.4 ms

No/diode

-25 °C...+50 °C

-25 °C...+40 °C

-40 °C...+85 °C

CE

EN 50178

300V

6.0kV

&gt;= 5.5 mm

IV

2

230 Vuc +5 %/-15 %

1.8 mA ac / 1.7 mA dc

395 mVA / 370 mW

20Hz dc, 5Hz ac

No

LED green

5...48 Vdc

20 mA

&lt; 1.6 V

0.16 mA

20 ms/20 ms

No/diode

-25 °C...+50 °C

-25 °C...+50 °C

-40 °C...+85 °C

CE

EN 50178

300V

6.0kV

&gt;= 5.5 mm

III

2

### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>  
Length x width x height mm

### Screw connection

4 / 0.50 / 4

77.0 x 6.0 x 62.0

### Screw connection

4 / 0.50 / 4

65.0 x 6.0 x 57.0

### Screw connection

4 / 0.50 / 4

65.0 x 6.0 x 57.0

### Ordering data

#### Connection technology

Screw connection

#### Type (Qty.=10) Order No.

DKO DK5 24VUC 8228630000

#### Type (Qty.=10) Order No.

DKO 35 115VUC 8077860000

#### Type (Qty.=10) Order No.

DKO 35 230VUC 8008160000

### Information

Input bottom

Input bottom

Input bottom

### Accessories

#### Information

End plate

AP DK5 8268870000

End plate

AP DK4 0687560000

End plate


AP DK4 0687560000

# EG-SERIES


## EG 7

- Combination foot for TS15, TS32 or TS35
- Optional pluggable on clip-in base RS EG7
- Width 10 mm
- Protective separation according to VDE 0884


## 5VDC



## 12VUC



## 24VUC



## Technical data

### Input

Rated voltage  
Rated current  
Power rating  
Max. input frequency  
Auxiliary voltage  
Status indicator

5 Vdc +/- 20 %  
6.8 mA  
40 mW  
15Hz  
No  
LED green

12 Vuc +/- 20 %  
33mA ac/30mA dc  
40 mW / 50 mVA  
15Hz  
No  
LED green

24 Vuc +/- 20 %  
3.4 mA dc/2.8 mA ac  
70 mW / 90 mVA  
15Hz  
No  
LED green

### Output

Output voltage  
Output current (max.)  
Voltage drop at max. load  
Block-state curr. (closed circuit curr.)  
Switch-on delay/Switch-off delay  
Short-circuit proof/Protective circuit

5...48Vdc  
100 mA  
< 50 µA  
6ms/12ms  
No/integrated freewheel diode

5...48Vdc  
100 mA  
< 1.5 V  
< =50 µA  
6ms/12ms  
No/integrated freewheel diode

5...48Vdc  
100 mA  
< 1.5 V  
< =50 µA  
5ms/15ms  
No/integrated freewheel diode

### General data

Ambient temp., fitted w. distance  
Ambient temp., fitted w/o distance  
Storage temperature  
Approvals

-25 °C...+60 °C  
-25 °C...+60 °C  
-40 °C...+60 °C  
CE

-25 °C...+60 °C  
-25 °C...+60 °C  
-40 °C...+60 °C  
CE

-25 °C...+60 °C  
-25 °C...+60 °C  
-40 °C...+60 °C  
CE

### Insulation coordinates (EN 50 178)

Standards  
Rated voltage  
Rated impulse voltage  
Creepage and clearance path input - output  
Overvoltage category  
Pollution severity

EN 50178  
300V  
6.0kV  
>= 5.5 mm  
III  
2

EN 50178  
300V  
6.0kV  
>= 5.5 mm  
III  
2

EN 50178  
300V  
6.0kV  
>= 5.5 mm  
III  
2

K

### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>  
Length x width x height mm

### Complete module Pluggable

1.50 / 0.50 / 1.50    2.50 / 0.50 / 2.50  
44.0 x 10.0 x 96.0    95.0 x 10.0 x 99.0

### Complete module Pluggable

1.50 / 0.50 / 1.50    2.50 / 0.50 / 2.50  
44.0 x 10.0 x 96.0    95.0 x 10.0 x 99.0

### Complete module Pluggable

1.50 / 0.50 / 1.50    2.50 / 0.50 / 2.50  
44.0 x 10.0 x 96.0    95.0 x 10.0 x 99.0

### Information

Dimensions pluggable opto-coupler  
incl. locking socket RS EG7

Dimensions pluggable opto-coupler  
incl. locking socket RS EG7

Dimensions pluggable opto-coupler  
incl. locking socket RS EG7

## Ordering data

### Article description

Complete module  
Pluggable

Type	(Qty.=10)	Order No.
EGO EG7 5VDC K-FU		8092490000
OST EG7 5VDC		8234560000

Type	(Qty.=10)	Order No.
EGO EG7 12VUC K-FU		8092510000
OST EG7 12VUC		8234570000

Type	(Qty.=10)	Order No.
EGO EG7 24VUC K-FU		8092530000
OST EG7 24VUC		8234580000

### Information

## Accessories

### Information

Locking socket  
RS EG7 8193830000

Locking socket  
RS EG7 8193830000


Locking socket  
RS EG7 8193830000

# EG-SERIES


## EG 7

- Combination foot for TS15, TS32 or TS35
- Optional pluggable on clip-in base RS EG7
- Width 10 mm
- Protective separation according to VDE 0884



## 48VUC



## 115VUC



## 230VAC



## Technical data

### Input

Rated voltage

Rated current

Power rating

Max. input frequency

Auxiliary voltage

Status indicator

### Output

Output voltage

Output current (max.)

Voltage drop at max. load

Block-state curr. (closed circuit curr.)

Switch-on delay/Switch-off delay

Short-circuit proof/Protective circuit

### General data

Ambient temp., fitted w. distance

Ambient temp., fitted w/o distance

Storage temperature

Approvals

### Insulation coordinates (EN 50 178)

Standards

Rated voltage

Rated impulse voltage

Creepage and clearance path input - output

Oversupply category

Pollution severity

### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>

Length x width x height mm

### Information

### Complete module

1.50 / 0.50 / 1.50 2.50 / 0.50 / 2.50

44.0 x 10.0 x 96.0 95.0 x 10.0 x 99.0

Dimensions pluggable opto-coupler incl. locking socket RS EG7

### Complete module

1.50 / 0.50 / 1.50 2.50 / 0.50 / 2.50

44.0 x 10.0 x 96.0 95.0 x 10.0 x 99.0

Dimensions pluggable opto-coupler incl. locking socket RS EG7

### Complete module

1.50 / 0.50 / 1.50 2.50 / 0.50 / 2.50

44.0 x 10.0 x 96.0 95.0 x 10.0 x 99.0

Dimensions pluggable opto-coupler incl. locking socket RS EG7

## Ordering data

### Article description

Complete module

Pluggable

### Type

(Qty.=10)

Order No.

EGO EG7 48VUC K-FU 8092550000

OST EG7 48VUC 8234590000

### Type

(Qty.=10)

Order No.

EGO EG7 115VUC K-FU 8092570000

OST EG7 115VUC 8234600000

### Type

(Qty.=10)

Order No.

EGO EG7 230VAC K-FU 8092590000

OST EG7 230VAC 8234610000

### Information

### Information

### Information

### Information

## Accessories

### Information

### Information

### Information

### Information

Locking socket  
RS EG7 8193830000

Locking socket  
RS EG7 8193830000


Locking socket  
RS EG7 8193830000

# EG-SERIES

## For long control wires

- For long control wires
- RC-Input circuit to disable interfering signals
  - Safe switching behavior in case of interfering pulses on the control side

## 230VAC RC



## Technical data

### Input

Rated voltage	230 Vac +6/-15 %
Rated current	3.8mA
Power rating	870 mVA
Max. input frequency	12Hz
Auxiliary voltage	No
Status indicator	LED green

### Output

Output voltage	5...48Vdc
Output current (max.)	100 mA
Voltage drop at max. load	< 1.5 V
Block-state curr. (closed circuit curr.)	< =50 µA
Switch-on delay/Switch-off delay	5ms/18ms
Short-circuit proof/Protective circuit	No/varistor, integral freewheeling diode

### General data

Ambient temp., fitted w. distance	-25 °C...+60 °C
Ambient temp., fitted w/o distance	-25 °C...+60 °C
Storage temperature	-40 °C...+60 °C
Approvals	CE

### Insulation coordinates (EN 50 178)

Standards	EN 50178
Rated voltage	300V
Rated impulse voltage	6.0kV
Creepage and clearance path input - output	>= 5.5 mm
Overshoot category	III
Pollution severity	2

K

### Dimensions

Clamping range (rating- / min. / max.) mm<sup>2</sup>  
Length x width x height mm

### Complete module      Pluggable

1.50 / 0.50 / 1.50	2.50 / 0.50 / 2.50
44.0 x 10.0 x 96.0	95.0 x 10.0 x 99.0

Dimensions pluggable opto-coupler  
incl. locking socket RS EG7

### Ordering data

Article description	Type	(Qty.=10)	Order No.
Complete module	EGO EG7 RC 230VAC	8387580000	
Pluggable	OST EG7 230VAC RC	8394990000	

### Information

### Accessories

#### Information

Locking socket  
RS EG7 8193830000