# Cree® XLamp® CXA1507 LED



#### **PRODUCT DESCRIPTION**

The XLamp® CXA1507 LED array expands Cree's family of high-flux, multi-die arrays in a smaller, easy-to-use platform. With XLamp LED lighting-class reliability, the CXA1507's small, uniform emitting surface enables both directional and non-directional lighting applications including lamp retrofit and luminaire designs. Available in 2-step, 3-step and 4-step color consistency, and featuring a 9-mm optical source, the CXA1507 brings new levels of flux and efficacy to this form factor.

#### The CX Family LED Design Guide

provides basic information on the requirements to use the CXA1507 LED successfully in luminaire designs.

# **FEATURES**

- Available in 4-step, 3-step and 2-step EasyWhite<sup>®</sup> bins at 2700 K, 3000 K, 3500 K, 4000 K & 5000 K CCT and 4-step EasyWhite bins at 5700 K & 6500 K CCT
- Available in ANSI white bins at 4000 K, 5000 K, 5700 K & 6500 K CCT
- Available in 70-, 80-, 90- and 93-minimum CRI options
- Forward voltage options: 18-V class & 36-V class
- 85 °C binning and characterization
- Maximum drive current: 750 mA (18 V), 375 mA (36 V)
- 115° viewing angle, uniform chromaticity profile
- Top-side solder connections
- Thermocouple attach point
- NEMA SSL-3 2011 standard flux bins
- RoHS and REACh compliant
- UL<sup>®</sup> recognized component (E349212)

6

#### **TABLE OF CONTENTS**

Characteristics2
Operating Limits3
Flux Characteristics, EasyWhite® Order
Codes and Bins - 18 V4
Flux Characteristics, ANSI White Order
Codes and Bins - 18 V7
Flux Characteristics, EasyWhite® Order
Codes and Bins - 36 V8
Flux Characteristics, ANSI White Order
Codes and Bins - 36 V 11
Relative Spectral Power Distribution 12
Electrical Characteristics 13
Relative Luminous Flux 14
Typical Spatial Distribution16
Performance Groups - Brightness 16
Performance Groups - Chromaticity 17
Cree EasyWhite® Bins Plotted on the
1931 CIE Color Space 20
Cree ANSI White Bins Plotted on the
1931 CIE Color Space 20
Bin and Order Code Formats 21
Mechanical Dimensions 21
Thermal Design 22
Notes 24
Packaging25

# Copyright © 2012-2017 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree®, XLamp® and EasyWhite® are registered trademarks and the Cree logo is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC.

#### **CHARACTERISTICS**

Characteristics	Unit	Minimum	Typical	Maximum
Viewing angle (FWHM)	degrees		115	
ESD withstand voltage (HBM per Mil-Std-883D)	V			8000
DC forward current (18 V)	mA			750*
DC forward current (36 V)	mA			375*
Reverse current 18 V, 36 V)	mA			0.1
Forward voltage (18 V, 400 mA, 85 °C)	V		17.5	
Forward voltage (18 V, 400 mA, 25 °C)	V			21
Forward voltage (36 V, 200 mA, 85 °C)	V		35	
Forward voltage (36 V, 200 mA, 25 °C)	V			42


\* Refer to the Operating Limits section.

XLAMP<sup>®</sup> CXA1507 LED



## **OPERATING LIMITS**

The maximum current rating of the CXA1507 is dependent on the case temperature (Tc) when the LED has reached thermal equilibrium under steady-state operation. The graphs shown below assume that the system design employs good thermal management (thermal interface material and heat sink) and may vary when poor thermal management is employed. Please refer to the Mechanical Dimensions section on page 21 for the location of the Tc measurement point.



Copyright © 2012-2017 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree®, XLamp® and EasyWhite® are registered trademarks and the Cree logo is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC.



# FLUX CHARACTERISTICS, EASYWHITE<sup>®</sup> ORDER CODES AND BINS - 18 V ( $I_F$ = 400 mA, $T_J$ = 85 °C)

The following table provides order codes for XLamp CXA1507 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 21).

Nominal	С	RI	Minin	num Lumino	ous Flux		2-Step		3-Step		4-Step
CCT	Min	Тур	Group	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	Group	Order Code	Group	Order Code	Group	Order Code
			G4	840	938						CXA1507-0000- 000F00G465F
	70	75	H2	900	1005					65F	CXA1507-0000- 000F00H265F
6500 K			H4	970	1084						CXA1507-0000- 000F00H465F
0000 K			G2	780	871						CXA1507-0000- 000F0HG265F
	80		G4	840	938					65F	CXA1507-0000- 000F0HG465F
			H2	900	1005						CXA1507-0000- 000F0HH265F
			G4	840	938						CXA1507-0000- 000F00G457F
	70	75	H2	900	1005					57F	CXA1507-0000- 000F00H257F
5700 K			H4	970	1084						CXA1507-0000- 000F00H457F
5700 K			G2	780	871						CXA1507-0000- 000F0HG257F
	80		G4	840	938					57F	CXA1507-0000- 000F0HG457F
			H2	900	1005						CXA1507-0000- 000F0HH257F
			G4	840	938		CXA1507-0000- 000F00G450H				CXA1507-0000- 000F00G450F
	70	75	H2	900	1005	50H	CXA1507-0000- 000F00H250H			50F	CXA1507-0000- 000F00H250F
			H4	970	1084		CXA1507-0000- 000F00H450H				CXA1507-0000- 000F00H450F
			G2	780	871		CXA1507-0000- 000F0HG250H				CXA1507-0000- 000F0HG250F
5000 K	80		G4	840	938	50H	CXA1507-0000- 000F0HG450H	50G	CXA1507-0000- 000F0HG450G	50F	CXA1507-0000- 000F0HG450F
			H2	900	1005		CXA1507-0000- 000F0HH250H		CXA1507-0000- 000F0HH250G		CXA1507-0000- 000F0HH250F
			F2	680	759		CXA1507-0000- 000F0UF250H				CXA1507-0000- 000F0UF250F
	90	95	F4	730	815	50H	CXA1507-0000- 000F0UF450H	50G	CXA1507-0000- 000F0UF450G	50F	CXA1507-0000- 000F0UF450F
			G2	780	871		CXA1507-0000- 000F0UG250H		CXA1507-0000- 000F0UG250G		CXA1507-0000- 000F0UG250F

Notes

Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).

• Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.

\* Flux values @ 25 °C are calculated and for reference only.

Nominal	С	RI	Minin	num Lumino	ous Flux		2-Step		3-Step		4-Step
CCT	Min	Тур	Group	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	Group	Order Code	Group	Order Code	Group	Order Code
			G4	840	938		CXA1507-0000- 000F00G440H				CXA1507-0000- 000F00G440F
	70	75	H2	900	1005	40H	CXA1507-0000- 000F00H240H			40F	CXA1507-0000- 000F00H240F
			H4	970	1084		CXA1507-0000- 000F00H440H				CXA1507-0000- 000F00H440F
			G2	780	871		CXA1507-0000- 000F0HG240H				CXA1507-0000- 000F0G240F
4000 K	80		G4	840	938	40H	CXA1507-0000- 000F0HG440H	40G	CXA1507-0000- 000F0HG440G	40F	CXA1507-0000- 000F0HG440F
			H2	900	1005		CXA1507-0000- 000F0HH240H		CXA1507-0000- 000F0HH240G		CXA1507-0000- 000F0HH240F
			E4	635	709		CXA1507-0000- 000F0UE440H				CXA1507-0000- 000F0UE440F
	90	95	F2	680	759	40H	CXA1507-0000- 000F0UF240H	40G	CXA1507-0000- 000F0UF240G	40F	CXA1507-0000- 000F0UF240F
			F4	730	815		CXA1507-0000- 000F0UF440H		CXA1507-0000- 000F0UF440G		CXA1507-0000- 000F0UF440F
			G2	780	871		CXA1507-0000- 000F00G235H				CXA1507-0000- 000F00G235F
	80		G4	840	938	35H	CXA1507-0000- 000F00G435H	35G	CXA1507-0000- 000F00G435G	35F	CXA1507-0000- 000F00G435F
3500 K			H2	900	1005		CXA1507-0000- 000F00H235H		CXA1507-0000- 000F00H235G		CXA1507-0000- 000F00H235F
3300 K			E2	590	659		CXA1507-0000- 000F0YE235H				CXA1507-0000- 000F0YE235F
	93	95	E4	635	709	35H	CXA1507-0000- 000F0YE435H	35G	CXA1507-0000- 000F0YE435G	35F	CXA1507-0000- 000F0YE435F
			F2	680	759		CXA1507-0000- 000F0YF235H		CXA1507-0000- 000F0YF235G		CXA1507-0000- 000F0YF235F
			F4	730	815		CXA1507-0000- 000F00F430H				CXA1507-0000- 000F00F430F
	80		G2	780	871	30H	CXA1507-0000- 000F00G230H	30G	CXA1507-0000- 000F00G230G	30F	CXA1507-0000- 000F00G230F
2000 K			G4	840	938		CXA1507-0000- 000F00G430H		CXA1507-0000- 000F00G430G		CXA1507-0000- 000F00G430F
3000 K			D4	550	614		CXA1507-0000- 000F0YD430H				CXA1507-0000- 000F0YD430F
	93	95	E2	590	659	30H	CXA1507-0000- 000F0YE230H	30G	CXA1507-0000- 000F0YE230G	30F	CXA1507-0000- 000F0YE230F
			E4	635	709		CXA1507-0000- 000F0YE430H		CXA1507-0000- 000F0YE430G		CXA1507-0000- 000F0YE430F

## FLUX CHARACTERISTICS, EASYWHITE<sup>®</sup> ORDER CODES AND BINS - 18 V (I<sub>F</sub> = 400 mA, T<sub>I</sub> = 85 °C) - CONTINUED

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).
- Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- \* Flux values @ 25 °C are calculated and for reference only.

Nominal	С	CRI Minimum Luminous Flux			2-Step		3-Step		4-Step		
CCT	Min	Тур	Group Flux (Im) @ 85 °C @ 25 °C* Group Order Code Gro		Group	Order Code	Group	Order Code			
			F4	730	815		CXA1507-0000- 000F00F427H				CXA1507-0000- 000F00F427F
	80		G2	780	871	27H	CXA1507-0000- 000F00G227H	27G	CXA1507-0000- 000F00G227G	27F	CXA1507-0000- 000F00G227F
0700 K			G4	840	938		CXA1507-0000- 000F00G427H	CXA1507-0000- 000F00G427G		CXA1507-0000- 000F00G427F	
2700 K			D2	510	569		CXA1507-0000- 000F0YD227H				CXA1507-0000- 000F0YD227F
	93	95	D4	550	614	27H	CXA1507-0000- 000F0YD427H	27G	CXA1507-0000- 000F0YD427G	27F	CXA1507-0000- 000F0YD427F
			E2	590	659		CXA1507-0000- 000F0YE227H		CXA1507-0000- 000F0YE227G		CXA1507-0000- 000F0YE227F

#### FLUX CHARACTERISTICS, EASYWHITE<sup>®</sup> ORDER CODES AND BINS - 18 V (I<sub>F</sub> = 400 mA, T<sub>I</sub> = 85 °C) - CONTINUED

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).
- Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- \* Flux values @ 25 °C are calculated and for reference only.



# FLUX CHARACTERISTICS, ANSI WHITE ORDER CODES AND BINS - 18 V (I<sub>F</sub> = 400 mA, T<sub>J</sub> = 85 °C)

The following table provides order codes for XLamp CXA1507 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 21).

Nominal	C	RI	М	inimum Luminous	Flux		
CCT	Min	Тур	Group	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	Chromaticity Regions	Order Code
			G4	840	938		CXA1507-0000-000F00G40E1
	70	75	H2	900	1005	1A0, 1B0, 1C0, 1D0, 65F	CXA1507-0000-000F00H20E1
6500 K			H4	970	1084		CXA1507-0000-000F00H40E1
0500 K			G2	780	871		CXA1507-0000-000F0HG20E1
	80		G4	840	938	1A0, 1B0, 1C0, 1D0, 65F	CXA1507-0000-000F0HG40E1
			H2	900	1005		CXA1507-0000-000F0HH20E1
			G4	840	938		CXA1507-0000-000F00G40E2
	70	75	H2	900	1005	2A0, 2B0, 2C0, 2D0, 57F	CXA1507-0000-000F00H20E2
5700 K			H4	970	1084		CXA1507-0000-000F00H40E2
5700 K			G2	780	871		CXA1507-0000-000F0HG20E2
	80		G4	840	938	2A0, 2B0, 2C0, 2D0, 57F	CXA1507-0000-000F0HG40E2
			H2	900	1005		CXA1507-0000-000F0HH20E2
			G4	840	938		CXA1507-0000-000F00G40E3
	70	75	H2	900	1005	3A0, 3B0, 3C0, 3D0, 50F	CXA1507-0000-000F00H20E3
5000 K			H4	970	1084		CXA1507-0000-000F00H40E3
3000 K			G2	780	871		CXA1507-0000-000F0HG20E3
	80		G4	840	938	3A0, 3B0, 3C0, 3D0, 50F 5A0, 5B0, 5C0, 5D0, 40F	CXA1507-0000-000F0HG40E3
			H2	900	1005		CXA1507-0000-000F0HH20E3
			G4	840	938		CXA1507-0000-000F00G40E5
4000 K	70	75	H2	900	1005		CXA1507-0000-000F00H20E5
			H4	970	1084		CXA1507-0000-000F00H40E5

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).
- Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- \* Flux values @ 25 °C are calculated and for reference only.



# FLUX CHARACTERISTICS, EASYWHITE<sup>®</sup> ORDER CODES AND BINS - 36 V ( $I_F$ = 200 mA, $T_J$ = 85 °C)

The following table provides order codes for XLamp CXA1507 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 21).

Nominal	C	RI	Minin	num Lumino	ous Flux		2-Step		3-Step		4-Step
CCT	Min	Тур	Group	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	Group	Order Code	Group	Order Code	Group	Order Code
			G4	840	938						CXA1507-0000- 000N00G465F
	70	75	H2	900	1005					65F	CXA1507-0000- 000N00H265F
6500 K			H4	970	1084						CXA1507-0000- 000N00H465F
0000 K			G2	780	871						CXA1507-0000- 000N0HG265F
	80		G4	840	938					65F	CXA1507-0000- 000N0HG465F
			H2	900	1005						CXA1507-0000- 000N0HH265F
			G4	840	938						CXA1507-0000- 000N00G457F
	70	75	H2	900	1005					57F	CXA1507-0000- 000N00H257F
5700 K			H4	970	1084						CXA1507-0000- 000N00H457F
5700 K			G2	780	871						CXA1507-0000- 000N0HG257F
	80		G4	840	938					57F	CXA1507-0000- 000N0HG457F
			H2	900	1005						CXA1507-0000- 000N0HH257F
			G4	840	938		CXA1507-0000- 000N00G450H				CXA1507-0000- 000N00G450F
	70	75	H2	900	1005	50H	CXA1507-0000- 000N00H250H			50F	CXA1507-0000- 000N00H250F
			H4	970	1084		CXA1507-0000- 000N00H450H				CXA1507-0000- 000N00H450F
			G2	780	871		CXA1507-0000- 000N0HG250H				CXA1507-0000- 000N0HG250F
5000 K	80		G4	840	938	50H	CXA1507-0000- 000N0HG450H	50G	CXA1507-0000- 000N0HG450G	50F	CXA1507-0000- 000N0HG450F
			H2	900	1005		CXA1507-0000- 000N0HH250H		CXA1507-0000- 000N0HH250G		CXA1507-0000- 000N0HH250F
			F2	680	759		CXA1507-0000- 000N0UF250H				CXA1507-0000- 000N0UF250F
	90	95	F4	730	815	50H	CXA1507-0000- 000N0UF450H	50G	CXA1507-0000- 000N0UF450G	50F	CXA1507-0000- 000N0UF450F
			G2	780	871		CXA1507-0000- 000N0UG250H		CXA1507-0000- 000N0UG250G		CXA1507-0000- 000N0UG250F

Notes

Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).

• Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.

\* Flux values @ 25 °C are calculated and for reference only.

Nominal	С	RI	Minin	num Lumino	ous Flux		2-Step		3-Step		4-Step
CCT	Min	Тур	Group	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	Group	Order Code	Group	Order Code	Group	Order Code
			G4	840	938		CXA1507-0000- 000N00G440H				CXA1507-0000- 000N00G440F
	70	75	H2	900	1005	40H	CXA1507-0000- 000N00H240H			40F	CXA1507-0000- 000N00H240F
			H4	970	1084		CXA1507-0000- 000N00H440H				CXA1507-0000- 000N00H440F
			G2	780	871		CXA1507-0000- 000N0HG240H				CXA1507-0000- 000N0G240F
4000 K	80		G4	840	938	40H	CXA1507-0000- 000N0HG440H	40G	CXA1507-0000- 000N0HG440G	40F	CXA1507-0000- 000N0HG440F
			H2	900	1005		CXA1507-0000- 000N0HH240H		CXA1507-0000- 000N0HH240G		CXA1507-0000- 000N0HH240F
			E4	635	709		CXA1507-0000- 000N0UE440H				CXA1507-0000- 000N0UE440F
	90	95	F2	680	759	40H	CXA1507-0000- 000N0UF240H	40G	CXA1507-0000- 000N0UF240G	40F	CXA1507-0000- 000N0UF240F
			F4	730	815		CXA1507-0000- 000N0UF440H		CXA1507-0000- 000N0UF440G		CXA1507-0000- 000N0UF440F
			G2	780	871		CXA1507-0000- 000N00G235H				CXA1507-0000- 000N00G235F
	80		G4	840	938	35H	CXA1507-0000- 000N00G435H	35G	CXA1507-0000- 000N00G435G	35F	CXA1507-0000- 000N00G435F
3500 K			H2	900	1005		CXA1507-0000- 000N00H235H		CXA1507-0000- 000N00H235G		CXA1507-0000- 000N00H235F
3300 K			E2	590	659		CXA1507-0000- 000N0YE235H				CXA1507-0000- 000N0YE235F
	93	95	E4	635	709	35H	CXA1507-0000- 000N0YE435H	35G	CXA1507-0000- 000N0YE435G	35F	CXA1507-0000- 000N0YE435F
			F2	680	759		CXA1507-0000- 000N0YF235H		CXA1507-0000- 000N0YF235G		CXA1507-0000- 000N0YF235F
			F4	730	815		CXA1507-0000- 000N00F430H				CXA1507-0000- 000N00F430F
	80		G2	780	871	30H	CXA1507-0000- 000N00G230H	30G	CXA1507-0000- 000N00G230G	30F	CXA1507-0000- 000N00G230F
3000 K			G4	840	938		CXA1507-0000- 000N00G430H		CXA1507-0000- 000N00G430G		CXA1507-0000- 000N00G430F
3000 K			D4	550	614		CXA1507-0000- 000N0YD430H				CXA1507-0000- 000N0YD430F
	93	95	E2	590	659	30H	CXA1507-0000- 000N0YE230H	30G	CXA1507-0000- 000N0YE230G	30F	CXA1507-0000- 000N0YE230F
			E4	635	709		CXA1507-0000- 000N0YE430H		CXA1507-0000- 000N0YE430G		CXA1507-0000- 000N0YE430F

## FLUX CHARACTERISTICS, EASYWHITE<sup>®</sup> ORDER CODES AND BINS - 36 V (I<sub>F</sub> = 200 mA, T<sub>J</sub> = 85 °C) - CONTINUED

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).
- Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- \* Flux values @ 25 °C are calculated and for reference only.

Nominal	С	CRI Minimum Luminous Flux 2-Step			3-Step	4-Step					
CCT	CT Min Typ		Group	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	Group	Order Code	Group	Order Code	Group	Order Code
			F4	730	815		CXA1507-0000- 000N00F427H				CXA1507-0000- 000N00F427F
	80		G2	780	871	27H	CXA1507-0000- 000N00G227H	27G	CXA1507-0000- 000N00G227G	27F	CXA1507-0000- 000N00G227F
0700 K			G4	840	938		CXA1507-0000- 000N00G427H		CXA1507-0000- 000N00G427G		CXA1507-0000- 000N00G427F
2700 K			D2	510	569		CXA1507-0000- 000N0YD227H				CXA1507-0000- 000N0YD227F
	93	95	D4	550	614	27H	CXA1507-0000- 000N0YD427H	27G	CXA1507-0000- 000N0YD427G	27F	CXA1507-0000- 000N0YD427F
			E2	590	659		CXA1507-0000- 000N0YE227H		CXA1507-0000- 000N0YE227G		CXA1507-0000- 000N0YE227F

#### FLUX CHARACTERISTICS, EASYWHITE<sup>®</sup> ORDER CODES AND BINS - 36 V (I<sub>F</sub> = 200 mA, T<sub>I</sub> = 85 °C) - CONTINUED

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).
- Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- \* Flux values @ 25 °C are calculated and for reference only.



# FLUX CHARACTERISTICS, ANSI WHITE ORDER CODES AND BINS - 36 V (I<sub>F</sub> = 200 mA, T<sub>J</sub> = 85 °C)


The following table provides order codes for XLamp CXA1507 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 21).

Nominal	C	RI	м	inimum Luminous	Flux		
CCT	Min	Тур	Group	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	Chromaticity Regions	Order Code
			G4	840	938		CXA1507-0000-000N00G40E1
	70	75	H2	900	1005	1A0, 1B0, 1C0, 1D0, 65F	CXA1507-0000-000N00H20E1
6500 K			H4	970	1084		CXA1507-0000-000N00H40E1
0500 K			G2	780	871		CXA1507-0000-000N0HG20E1
	80		G4	840	938	1A0, 1B0, 1C0, 1D0, 65F	CXA1507-0000-000N0HG40E1
			H2	900	1005		CXA1507-0000-000N0HH20E1
			G4	840	938		CXA1507-0000-000N00G40E2
	70	75	H2	900	1005	2A0, 2B0, 2C0, 2D0, 57F	CXA1507-0000-000N00H20E2
5700 K			H4	970	1084		CXA1507-0000-000N00H40E2
5700 K			G2	780	871		CXA1507-0000-000N0HG20E2
	80		G4	840	938	2A0, 2B0, 2C0, 2D0, 57F	CXA1507-0000-000N0HG40E2
			H2	900	1005		CXA1507-0000-000N0HH20E2
			G4	840	938		CXA1507-0000-000N00G40E3
	70	75	H2	900	1005	3A0, 3B0, 3C0, 3D0, 50F	CXA1507-0000-000N00H20E3
5000 K			H4	970	1084		CXA1507-0000-000N00H40E3
3000 K			G2	780	871		CXA1507-0000-000N0HG20E3
	80		G4	840	938	3A0, 3B0, 3C0, 3D0, 50F 5A0, 5B0, 5C0, 5D0, 40F	CXA1507-0000-000N0HG40E3
			H2	900	1005		CXA1507-0000-000N0HH20E3
			G4	840	938		CXA1507-0000-000N00G40E5
4000 K	70	75	H2	900	1005		CXA1507-0000-000N00H20E5
			H4	970	1084		CXA1507-0000-000N00H40E5

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ±2 on CRI measurements. See the Measurements section (page 24).
- Cree XLamp CXA1507 LED order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- \* Flux values @ 25 °C are calculated and for reference only.


## **RELATIVE SPECTRAL POWER DISTRIBUTION**

The following graph is the result of a series of pulsed measurements at 400 mA for the 18-V CXA1507 LED and 200 mA for the 36-V CXA1507 LED and T<sub>1</sub> = 85 °C.



#### **ELECTRICAL CHARACTERISTICS**

The following graphs are the result of a series of steady-state measurements.






## **RELATIVE LUMINOUS FLUX**

The relative luminous flux values provided below are the ratio of:

- · Measurements of CXA1507 at steady-state operation at the given conditions, divided by
- Flux measured during binning, which is a pulsed measurement at 400 mA at T<sub>J</sub> = 85 °C for the 18-V CXA1507 LED.

Using the 18-V CXA1507 LED as an example, at steady-state operation of Tc = 25 °C,  $I_F = 650$  mA, the relative luminous flux ratio is 160% in the chart below. A CXA1507 LED that measures 710 Im during binning will deliver 1136 Im (710 \* 1.6) at steady-state operation of Tc = 25 °C,  $I_F = 650$  mA.




#### **RELATIVE LUMINOUS FLUX - CONTINUED**


The relative luminous flux values provided below are the ratio of:

- · Measurements of CXA1507 at steady-state operation at the given conditions, divided by
- Flux measured during binning, which is a pulsed measurement at 200 mA at T<sub>1</sub> = 85 °C for the 36-V CXA1507 LED.

Using the 36-V CXA1507 LED as an example, at steady-state operation of Tc = 25 °C,  $I_F = 325$  mA, the relative luminous flux ratio is 150% in the chart below. A CXA1507 LED that measures 710 lm during binning will deliver 1136 lm (710 \* 1.6) at steady-state operation of Tc = 25 °C,  $I_F = 325$  mA.



# **TYPICAL SPATIAL DISTRIBUTION**



## PERFORMANCE GROUPS - BRIGHTNESS (18 V, $I_F = 400 \text{ mA}$ ; 36 V, $I_F = 200 \text{ mA}$ , $T_J = 85 \text{ °C}$ )

XLamp CXA1507 LEDs are tested for luminous flux and placed into one of the following bins.

Group Code	Minimum Luminous Flux	Maximum Luminous Flux
D2	510	550
D4	550	590
E2	590	635
E4	635	680
F2	680	730
F4	730	780
G2	780	840
G4	840	900
H2	900	970
H4	970	1040
J2	1040	1120



# **PERFORMANCE GROUPS - CHROMATICITY (T<sub>J</sub> = 85 °C)**

XLamp CXA1507 LEDs are tested for chromaticity and placed into one of the regions defined by the following bounding coordinates.

EasyWhite Color Temperatures – 2-Step											
Code	ССТ	x	у								
		0.3429	0.3507								
50H	5000 K	0.3434	0.3571								
DUH	2000 K	0.3475	0.3604								
		0.3469	0.3539								
		0.3784	0.3741								
40H	4000 K	0.3804	0.3818								
400	4000 K	0.3867	0.3857								
		0.3844	0.3778								
		0.4030	0.3857								
35H	2500 K	0.4061	0.3941								
300	3500 K	0.4132	0.3976								
		0.4099	0.3890								
		0.4291	0.3973								
30H	3000 K	0.4333	0.4062								
30H	3000 K	0.4395	0.4084								
		0.4351	0.3994								
		0.4528	0.4046								
27H	2700 K	0.4578	0.4138								
2/11	2700 K	0.4638	0.4152								
		0.4586	0.4060								

EasyWhite Color Temperatures – 3-Step Ellipse						
Bin Code	ССТ	Center Point		Major Axis	Minor Axis	Rotation Angle
		x	у	а	b	(°)
50G	5000 K	0.3447	0.3553	0.00840	0.00312	65.0
40G	4000 K	0.3818	0.3797	0.00939	0.00402	53.7
35G	3500 K	0.4073	0.3917	0.00927	0.00414	54.0
30G	3000 K	0.4338	0.4030	0.00834	0.00408	53.2
27G	2700 K	0.4577	0.4099	0.00834	0.00420	48.5



# PERFORMANCE GROUPS - CHROMATICITY (T<sub>J</sub> = 85 °C) - CONTINUED

EasyWhite Color Temperatures – 4-Step					
Code	ССТ	x	у		
		0.3097	0.3196		
655	6500 K	0.3079	0.3297		
65F		0.3164	0.3382		
		0.3176	0.3275		
		0.3253	0.3325		
57F	5700 K	0.3249	0.3439		
57F		0.3331	0.3514		
		0.3330	0.3393		
		0.3407	0.3459		
50F	5000 K	0.3415	0.3586		
JUF	5000 K	0.3499	0.3654		
		0.3484	0.3521		
		0.3744	0.3685		
40F	4000 K	0.3782	0.3837		
40F		0.3912	0.3917		
		0.3863	0.3758		
		0.3981	0.3800		
35F	2500 K	0.4040	0.3966		
30F	3500 K	0.4186	0.4037		
		0.4116	0.3865		
		0.4242	0.3919		
30F	3000 K	0.4322	0.4096		
30F	3000 K	0.4449	0.4141		
		0.4359	0.3960		
		0.4475	0.3994		
27F	2700 K	0.4573	0.4178		
2/F	2700 K	0.4695	0.4207		
		0.4589	0.4021		



# **PERFORMANCE GROUPS - CHROMATICITY (T**<sub>J</sub> = 85 °C) - CONTINUED

ANSI White Bins				
Code	ССТ	Bin Code	x	у
	6500 K	1A0	0.3048	0.3207
			0.3130	0.3290
			0.3144	0.3186
			0.3068	0.3113
		1B0	0.3028	0.3304
			0.3115	0.3391
			0.3130	0.3290
0E1			0.3048	0.3207
UET		1C0	0.3115	0.3391
			0.3205	0.3481
			0.3213	0.3373
			0.3130	0.3290
		1D0	0.3130	0.3290
			0.3213	0.3373
			0.3221	0.3261
			0.3144	0.3186

Code	ССТ	Bin Code	x	у	
0E2	5700 K	2A0	0.3215	0.3350	
			0.3290	0.3417	
			0.3290	0.3300	
			0.3222	0.3243	
		2B0	0.3207	0.3462	
			0.3290	0.3538	
			0.3290	0.3417	
			0.3215	0.3350	
		2C0	0.3290	0.3538	
			0.3376	0.3616	
			0.3371	0.3490	
			0.3290	0.3417	
		2D0	0.3290	0.3417	
			0.3371	0.3490	
			0.3366	0.3369	
			0.3290	0.3300	
ANSI White Bins					
Code	сст	Bin Code	x	у	
		5A0	.3670	.3578	
			.3702	.3722	
			.3825	.3798	

.3783 .3646

.3702

.3736

.3869

.3825

.3825

.3869

.4006

.3950

.3783

.3825

.3950

.3898

5B0

5C0

5D0

4000 K

0E5

.3722

.3874

.3958

.3798

.3798

.3958

.4044

.3875

.3646

.3798

.3875

.3716

ANSI White Bins

1


ANSI White Bins				
Code	ССТ	Bin Code	x	у
	5000 K	3A0	.3371	.3490
			.3451	.3554
			.3440	.3427
			.3366	.3369
0E3		3B0	.3376	.3616
			.3463	.3687
			.3451	.3554
			.3371	.3490
		3C0	.3463	.3687
			.3551	.3760
			.3533	.3620
			.3451	.3554
		3D0	.3451	.3554
			.3533	.3620
			.3515	.3487
			.3440	.3427

Copyright @ 2012-2017 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree®, XLamp® and EasyWhite® are registered trademarks and the Cree logo is a	
trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC.	


XLAMP<sup>®</sup> CXA1507 LED



## CREE EASYWHITE® BINS PLOTTED ON THE 1931 CIE COLOR SPACE (T, = 85 °C)



# CREE ANSI WHITE BINS PLOTTED ON THE 1931 CIE COLOR SPACE (T<sub>j</sub> = 85 °C)




Copyright © 2012-2017 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree®, XLamp® and EasyWhite® are registered trademarks and the Cree logo is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC.


CREE 🚖

#### **BIN AND ORDER CODE FORMATS**

Bin codes and order codes are configured as follows:



## **MECHANICAL DIMENSIONS**



To

R c-a

Та

Tc

R\_tim

R\_hs

Та


#### THERMAL DESIGN

The CXA family of LED arrays can include over a hundred different LED die inside one package, and thus over a hundred different junction temperatures (T<sub>j</sub>). Cree has intentionally removed junction-temperature-based operating limits and replaced the commonplace maximum T<sub>j</sub> calculations with maximum ratings based on forward current ( $I_F$ ) and case temperature (Tc). No additional calculations are required to ensure the CXA LED is being operated within its designed limits. Please refer to page 3 for the Operating Limit specification.

There is no need to calculate for  $T_J$  inside the package, as the thermal management design process, specifically from solder point ( $T_{sp}$ ) to ambient ( $T_a$ ), remains identical to any other LED component. For more information on thermal management of Cree XLamp LEDs, please refer to the Thermal Management application note. For CXA soldering recommendations and more information on thermal interface materials (TIM) and connection methods, please refer to the Cree CX Family LEDs soldering and handling document. The CX Family LED Design Guide provides basic information on the requirements to use Cree XLamp CXA LEDs successfully in luminaire designs.


To keep the CXA1507 LED at or below the maximum rated Tc, the case to ambient temperature thermal resistance (R\_c-a) must be at or below the maximum R\_c-a value shown on the following graphs, depending on the operating environment. The y-axis in the graphs is a base 10 logarithmic scale.

As the figure at right shows, the R\_c-a value is the sum of the thermal resistance of the TIM (R\_tim) plus the thermal resistance of the heat sink (R\_hs).





## **THERMAL DESIGN - CONTINUED**



#### **NOTES**

#### Measurements

The luminous flux, radiant power, chromaticity, forward voltage and CRI measurements in this document are binning specifications only and solely represent product measurements as of the date of shipment. These measurements will change over time based on a number of factors that are not within Cree's control and are not intended or provided as operational specifications for the products. Calculated values are provided for informational purposes only and are not intended as specifications.

#### **Pre-Release Qualification Testing**

Please read the LED Reliability Overview for details of the qualification process Cree applies to ensure long-term reliability for XLamp LEDs and details of Cree's pre-release qualification testing for XLamp LEDs.

#### Lumen Maintenance

Cree now uses standardized IES LM-80-08 and TM-21-11 methods for collecting long-term data and extrapolating LED lumen maintenance. For information on the specific LM-80 data sets available for this LED, refer to the public LM-80 results document.

Please read the Long-Term Lumen Maintenance application note for more details on Cree's lumen maintenance testing and forecasting. Please read the Thermal Management application note for details on how thermal design, ambient temperature, and drive current affect the LED junction temperature.

#### **RoHS Compliance**

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree representative or from the Product Documentation sections of www.cree.com.

#### **REACh Compliance**

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Cree representative to insure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

#### **UL® Recognized Component**

Level 4 enclosure consideration. The LED package or a portion thereof has been investigated as a fire and electrical enclosure per ANSI/ UL 8750.

#### Vision Advisory

WARNING: Do not look at an exposed lamp in operation. Eye injury can result. For more information about LEDs and eye safety, please refer to the LED Eye Safety application note.

### PACKAGING

Cree CXA1507 LEDs are packaged in trays of 20. Five trays are sealed in an anti-static bag and placed inside a carton, for a total of 100 LEDs per carton. Each carton contains 100 LEDs from the same performance bin.

Dimensions are in inches. Tolerances:  $\pm$ .13 x°  $\pm$ 1°

