

# AVX High Reliability Tantalum Capacitors



Version 17.11

www.avx.com



# Contents



---

|  |                |
|--|----------------|
| Introduction.....  | 2              |
| High Reliability Tantalum Applications.....  | 3              |
| High Reliability Tantalum Chip Specifications.....   | 4-5            |
| Group A Test Options.....  | 6              |
| High Reliability Specification Requirements Comparison Chart.....                              | 6              |
| High Reliability Tantalum Chip Product Family - Design Guide.....                              | 7              |
| Part Numbering, Test & Packaging Options.....  | 8              |
| <b>TAZ Series.....</b>   | <b>9-30</b>    |
| <b>CWR09</b> – MIL-PRF-55365/4 Established Reliability, COTS-Plus & Space Level.....           | <b>9-12</b>    |
| <b>CWR19</b> – MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level.....          | <b>13-16</b>   |
| <b>CWR29</b> – MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level.....          | <b>17-22</b>   |
| <b>TAZ HRC5000 Medical Implantable Grade</b> .....   | <b>23-27</b>   |
| <b>TAZ HRC6000 Medical Implantable Grade</b> .....   | <b>28-30</b>   |
| <b>TCP SERIES - DSCC 09009.....</b>  | <b>31-33</b>   |
| <b>TBJ Series.....</b>   | <b>34-61</b>   |
| <b>CWR11</b> – MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level.....           | <b>34-37</b>   |
| <b>COTS-PLUS</b> .....   | <b>38-48</b>   |
| <b>COTS-PLUS</b> – SRC9000 Space Level.....  | <b>49-55</b>   |
| <b>DSCC Dwgs 07016 &amp; 95158</b> .....   | <b>56-61</b>   |
| <b>T4J HRC4000 Implantable Non Life Support and Non Implantable Life Support.....</b>          | <b>62-66</b>   |
| <b>TBM Multianode.....</b>   | <b>67-72</b>   |
| <b>Tantalum Ultra Low ESR &amp; Space Level</b> .....  | <b>67-69</b>   |
| <b>Tantalum Ultra Low ESR COTS-Plus</b> .....  | <b>70-72</b>   |
| <b>TBC Series.....</b>   | <b>73-84</b>   |
| <b>CWR15</b> – MIL-PRF-55365/12 Established Reliability, COTS-Plus & Space Level.....          | <b>73-75</b>   |
| <b>COTS-PLUS</b> .....   | <b>76-78</b>   |
| <b>TBC HRC5000 Medical Implantable Grade</b> .....   | <b>79-81</b>   |
| <b>TBC HRC6000 Next Generation Medical Implantable Grade</b> .....                             | <b>82-84</b>   |
| <b>T4C Series Implantable Non-Life Support and Non Implantable Life Support.....</b>           | <b>85-87</b>   |
| <b>TCB Series - Polymer COTS-Plus.....</b>   | <b>88-91</b>   |
| <b>TCS Series - COTS-Plus Polymer Solid Electrolytic Multianode Capacitor.....</b>             | <b>92-94</b>   |
| <b>DSCC 93026.....</b>   | <b>95-97</b>   |
| <b>TWA Series – COTS-Plus Wet Electrolytic Tantalum Capacitor.....</b>                         | <b>98-102</b>  |
| <b>TWA-Y 200° Series – Wet Electrolytic Tantalum Capacitor.....</b>                            | <b>103-106</b> |
| <b>TWA-X Series with Extension to 230°C – Wet Electrolytic Tantalum Capacitor.....</b>         | <b>107-109</b> |
| <b>TWS Wet Electrolytic Tantalum Capacitor – DSCC 13017.....</b>                               | <b>110-112</b> |
| <b>TWC Series.....</b>   | <b>113-129</b> |
| <b>MIL-PRF-39006 Series</b> – Military Conventional Wet Tantalum.....                          | <b>113-120</b> |
| <b>COTS-PLUS</b> – Conventional Wet Tantalum.....  | <b>121-127</b> |
| <b>High Temperature</b> – COTS-Plus 200°C Wet Tantalum.....                                    | <b>128-129</b> |
| <b>TWD High Temp Max Cap (HTMC) Series</b> – Wet Tantalum Super Capacitor.....                 | <b>130-131</b> |
| <b>TWM Module.....</b>   | <b>132-134</b> |
| <b>TAJ ESCC Tantalum Capacitor.....</b>  | <b>135-136</b> |
| <b>TES Low ESR – QPL ESCC Tantalum Chip Capacitor.....</b>                                     | <b>137-139</b> |
| <b>TAJ CECC Tantalum Capacitor.....</b>  | <b>140-141</b> |
| <b>TCH Low ESR Hermetic Series.....</b>  | <b>142-145</b> |
| <b>THH 230°C Hermetic Series.....</b>  | <b>146-149</b> |
| <b>High Reliability Tantalum MSL</b> – Storage, Bake out, and Handling Recommendations.....    | <b>150</b>     |
| <b>TAZ Series</b> - Tape & Reel Packaging.....   | <b>151</b>     |
| <b>TAJ, TBJ, T4J, TBM, TES, TBC, T4C and TCB Series</b> – Tape & Reel Packaging.....           | <b>152</b>     |
| <b>TCH and THH</b> – Packaging.....  | <b>153</b>     |
| <b>Tantalum Wet Electrolytic Capacitor</b> – Technical Summary and Application Guidelines..... | <b>154-159</b> |

## Introduction

### INTRODUCTION

AVX's **Biddeford, Maine** facility is the leading supplier of high reliability tantalum chips to the medical, military and aerospace industry.

As tantalum technology continues to develop, we are able to offer extended ratings in our products by providing more downsizing opportunities, higher capacitance ratings, new case sizes and low ESR options for critical output filtering applications. Combining this with in-line reliability grading capability for all chip capacitor series, we are able to supply these products to the most demanding applications.

- AS9100**  
standardized Quality Management System for the aerospace industry
- ISO 9001**  
fundamental Quality Management System designed to meet regulations & customer needs
- ISO 14001**  
Environmental Management System designed to help improve resource efficiency and reduce waste
- ISO 13485**  
Quality Management System for the design & manufacture of medical devices
- MIL-PRF-39006**  
military performance specification for established & high reliability electrolytic (wet) tantalum capacitors
- MIL-PRF-55365**  
military performance specification for established & high reliability solid tantalum capacitors
- MIL-STD-790**  
established & high reliability QPL standards

Our facility in **Lanskroun, Czech Republic** is AVX's manufacturing location for production of high end SMD & wet tantalum capacitors including automotive, medical, industrial, and specialty applications. Lanskroun is a European Space Agency (ESA) approved facility for manufacturing of ESCC 3012 SMD tantalum capacitors including detail specification ESCC 3012/001 TAJ-ESA series and ESCC 3012/004 TES low ESR and high CV SMD tantalum capacitors. Specialty applications include industry unique hermetically sealed SMD tantalum capacitors THH with continuous operation temperature up to 230°C and TCH series of low ESR hermetically sealed SMD polymer capacitors for mission critical applications.

- TS 16949**  
Quality Management System for automotive manufacturers & their supply chain
- ISO 9001**  
fundamental Quality Management System designed to meet regulations & customer needs
- ISO 14001**  
Environmental Management System designed to help improve resource efficiency and reduce waste
- ESCC 3012**  
ESA specification for electrical components in space applications
- ESCC 3012/001**  
ESA specification for electrical components in space applications for TAJ style caps
- ESCC 3012/004**  
ESA specification for electrical components in space applications for TES style caps
- CECC 3081**  
European military standard for electrical component production

### HIGH RELIABILITY TANTALUM

#### COTS-Plus

| Surface Mount MnO <sub>2</sub> Tantalum | Tantalum Microchip | Wet Tantalum                  | Solid Electrolytic Polymer |
|---|--------------------|-------------------------------|----------------------------|
| TCP Module Series                       | TBC Microchip      | TWA Series                    | TCB Series                 |
| TAZ Series                              |                    | TWC Conventional Wet Tantalum | TCS Series                 |
| TBJ Series                              |                    | TWS Series                    |                            |
| TBM Multianode                          |                    | TWM Module                    |                            |
| TAJ CECC Series                         |                    | TWD Max Cap                   |                            |

#### Military

| MIL-PRF-55365            | MIL-PRF-39006   | DSCC  |
|--------------------------|-----------------|-------|
| 55365/4 CWR09            | CLR79 M39006/22 | 09009 |
| 55365/8 CWR11            | CLR81 M39006/25 | 07016 |
| 55365/11 CWR19, 29       | CLR90 M39006/30 | 95158 |
| 55365/12 CWR15 Microchip | CLR91 M39006/31 | 93026 |
|                          |                 | 13017 |

#### Aerospace

| MIL-PRF-55365 "T" Space Level | SRC9000 Space Level   | Hermetically Sealed         | European Space Components Coordination (ESCC) |
|-------------------------------|-----------------------|-----------------------------|---|
| 55365/4 CWR09                 | TAZ SRC9000           | THH 230°C Hermetic Series   | TAJ Series                                    |
| 55365/8 CWR11                 | TBC Microchip SRC9000 | TCH Low ESR Hermetic Series | TES Low ESR                                   |
| 55365/11 CWR19, 29            | TBJ SRC9000           | TWC SRW9000                 |   |
| 55365/12 CWR15 Microchip      | TBM SRC9000           | TWS SRW9000                 |   |
|                               | TCP SRC9000 Module    |                             |   |


#### Medical

| Implantable & Life Sustaining | Other Medical Applications   |
|-------------------------------|------------------------------|
| TBC Microchip HRC6000 Series  | T4J HRC4000 Series           |
| TAZ HRC6000 Series            | T4C Microchip HRC4000 Series |
| TBC Microchip HRC5000 Series  |                              |
| TAZ HRC5000 Series            |                              |


#### High Temperature Applications

| Wet Tantalum                  | Surface Mount MnO <sub>2</sub> Tantalum |
|-------------------------------|---|
| TWA 200°C Series              | THH 230°C Hermetic Series               |
| TWA 230°C Series              |   |
| TWC 200°C Conventional Wet Ta |   |


### HIGH RELIABILITY TANTALUM CHIP SPECIFICATIONS



### CZECH REPUBLIC HIGH RELIABILITY TANTALUM CHIP SPECIFICATIONS



### HIGH RELIABILITY WET TANTALUM SPECIFICATIONS



### GROUP A TEST OPTIONS

| TEST  | Group A Testing comparison   |                              |                           |                           |
|---|------------------------------|------------------------------|---------------------------|---------------------------|
|   | AVX COTS-Plus                | MIL-PRF-55365 QPL            |                           | AVX SRC9000 Space Level   |
|   |                              | MIL Weibull B, C, D          | MIL T Level               |                           |
| 100% Reflow   | ✓                            | ✓                            | ✓                         | ✓                         |
| 100% Thermal Shock                                      | ✓                            | ✓                            | ✓                         | ✓                         |
| 100% Weibull  | Optional                     | Mandatory                    | Mandatory-Grade C min     | Mandatory-Grade C min     |
| 100% Surge Current                                      | Optional                     | Optional                     | Mandatory - C Level       | Mandatory - C Level       |
| 100% Electrical Testing                                 | Custom Test Limits Available | To Specification Limits Only | +3 Sigma Limits           | +3 Sigma Limits or Custom |
| Visual & Mechanical                                     | Sample                       | Sample                       | 100% - 20X                | 100% - 20X                |
| Simulated Mounting, Rework and Lot Conformance (Sample) | Optional                     |                              |                           | ✓                         |
| Solderability Test* (Sample)                            | Optional<br>75% Coverage     | Mandatory<br>95% Coverage    | Mandatory<br>95% Coverage | Mandatory<br>95% Coverage |
| 100% X-Ray  | Optional                     |                              | ✓                         | ✓                         |
| DPA - 1580 Destructive Physical Analysis                | Optional                     |                              | ✓                         | ✓                         |
| Surge Voltage (Sample)                                  | Optional                     |                              |                           | ✓                         |
| Hot DC Leakage (Sample)                                 | Optional                     |                              |                           | ✓                         |
| Temperature Stability (Sample)                          | Optional                     | Mandatory                    | Mandatory                 | Mandatory                 |

\*Only Mil QPL ratings receive the steam age portion of solderability testing unless otherwise specified by the customer  
 \*\*Medical Grade Group A test procedures, contact AVX

### HIGH RELIABILITY SPECIFICATION REQUIREMENTS COMPARISON CHART


| TEST              |               | AVX Series            | 100% Reflow | Vibration | Shock or Bump | 100% Thermal Shock | Resistance to Soldering Heat | Moisture Resistance | Operating Life | 100% Weibull | 100% Surge Current | 100% Electrical Testing | Visual & Mechanical | Simulated Mounting, Rework and Accelerated Life | Solderability Test* | 100% X-Ray | DPA - 1580 Destructive Physical Analysis | Surge Voltage | Hot DC Leakage | Temperature Stability | Burn-in 168hrs | Adhesion (shear) | Climatiquae Sequence *** |
|-------------------|---------------|-----------------------|-------------|-----------|---------------|--------------------|------------------------------|---------------------|----------------|--------------|--------------------|-------------------------|---------------------|---|---------------------|------------|--|---------------|----------------|-----------------------|----------------|------------------|--------------------------|
| MIL PRF 55365 QPL | Standard MIL  | CWR09, 11, 15, 19, 29 | 0 ■         | ■ X       |               | 0 ■                | ■ X                          | ■ X                 | ■ X            | 0 ■          | ▲                  | 0 ■                     | 0 ■ X               |   | ■ X ▲               |            |  | ■ X           |                | 0 ■ X                 |                |                  |                          |
|                   | New "T" level | CWR09, 11, 15, 19, 29 | 0 ■         | ■ X       |               | 0 ■                | ■ X                          | ■ X                 | 0 ■ X          | 0 ■          | 0 ■                | 0 ■                     | 0 ■                 |   | ■ X ▲               | 0 ■        | 0 X                                      | ■ X           |                | 0 ■ X                 |                |                  |                          |
| Space Level       | AVX SRC9000** | TBJ/TBM (COTS)        | 0           | ▲ X       | ▲ X           | 0                  | ▲ X                          | ▲ X                 | (*)0 ▲ X       | 0            | 0                  | 0 ▶                     | 0                   | 0 X   | 0 X                 | 0          | 0 X                                      | 0 X           | 0 X            | 0 X                   |                | ▲ X              |                          |
|                   | AVX SRC9000** | TAZ/TBC/TBJ (MIL)     | 0 ■         | ▲ ■ X     | ▲ X           | 0 ■                | ▲ ■ X                        | ▲ ■ X               | ▲ ■ X          | 0 ■          | 0 ■                | 0 ■ ▶                   | 0 ■                 | 0 X   | 0 ■ X               | 0 ■        | 0 X                                      | 0 ■ X         | 0 ■ X          | 0 ■ X                 | 0 ■ X          |                  | ▲ X                      |
| AVX COTS-Plus     | COTS-Plus**   | TBJ/TBM/TAZ           | 0           |           |               | 0                  |                              |                     |                | ▲            | 0                  | 0 X                     |                     |   | ▲ X                 |            |  |               |                |                       | ▲ X            |                  |                          |
|                   | DSCC 07016    | TBJ                   | 0           | ▲ X       |               | 0                  | ▲ X                          | ▲ X                 | ▲ X            | ▲            | ▲                  | 0                       | 0 X                 |   | ▲ X                 |            |  | ▲ X           |                | ▲ X                   |                |                  |                          |
|                   | DSCC 95158    | TBJ                   | 0           | ▲ X       |               | 0                  | ▲ X                          | ▲ X                 | ▲ X            | ▲            | ▲                  | 0                       | 0 X                 |   | ▲ X                 |            |  | ▲ X           |                | ▲ X                   |                |                  |                          |
|                   | COTS-Plus     | TCS                   | 0           | ■ X       | ■ X           | 0                  |                              |                     | ■ X            |              | 0                  | 0 ▲                     | 0 X                 |   | 0 X                 | 0 X        | 0  | 0             | 0 ▲            | 0 ▲                   | ■ X            |                  |                          |
| ESA-ESCC3012      | LAT 1         | TAJ-ESA, TES          | 0 ●         | 0         | 0             | 0 ●                |                              |                     | 0              |              | ●                  | 0 ●                     | 0                   | 0   | 0 ●                 | level B ●  |  | 0             |                | 0                     | 0              | 0                | 0                        |
|                   | LAT 2         |                       | 0 ●         |           |               | ●                  |                              |                     | 0              |              | ●                  | 0 ●                     | 0                   | 0   | 0 ●                 | level B ●  |  | 0             |                | 0                     | 0              | 0                | 0                        |
|                   | LAT 3         |                       | ●           |           |               | ●                  |                              |                     |                |              | ●                  | 0 ●                     | 0                   | 0   | 0 ●                 | level B ●  |  | 0             |                | 0                     | 0              | 0                | 0                        |
|                   | NO LAT        |                       | ●           |           |               | ●                  |                              |                     |                |              | ●                  | 0 ●                     | 0                   | 0   | 0 ●                 | level B ●  |  | 0             |                | 0                     | 0              | 0                | 0                        |

\*Only Mil QPL ratings receive the steam age portion of solderability testing unless otherwise specified by the customer  
 \*\*Testing of low ESR components requiring a mounted sample shall allow a 2X increase in catalog ESR for post measurements  
 \*\*\* = Dry Heat, Damp Heat, Storage, Low Air Pressure, Damp Heat

- 0 Standard Test
- ▲ Optional Test
- Qualification and or GRP C
- X Sample Test
- ★ COTS Upscreen 1000Hr 125°C
- ▶ AVX Standard DCL/ESR/DF 3 SIGMA
- ◆ DLA Standard DCL/ESR 3 SIGMA
- Part of Manufacturing Flow (PID)
- ▲ AVX Standard DCL 3 SIGMA


### HIGH RELIABILITY TANTALUM CHIP PRODUCT FAMILY - DESIGN GUIDE

#### TAZ Series Case Size



TCP Module

#### TBC Series Case Sizes



#### TAZ FAMILY SIZES:

##### CWR09, CWR19, CWR29 and TCP Modules


The TAZ family boasts the widest range of case sizes and fullest range of MIL-QPL qualifications of any tantalum chip family, making it the ideal choice for the MIL-Aerospace designer.

This family represents the most flexible of surface mount form factors. The case sizes originate from the original MIL chip sizes, enabling support for all legacy programs, but have been extended to include both smaller and larger case size options. There are ten case sizes covering the full Capacitance/Voltage range. Parts are suited to hybrid or PCB assembly, with case sizes A to E designed as low profile (.050" nom).

The Low ESR versions of the larger case sizes are ideally suited to power applications, and the H case is also footprint compatible with TBJ D / E case sizes.

This family is also the ideal replacement for conformal coated CWR06 styles in mechanically demanding applications.

#### TBJ Series Case Size



#### TBJ FAMILY SIZES:

##### DSCC 95158, 07016 & CWR11; TBM Ultra-Low ESR.

The TBJ family is based on EIA / Industrial standard sizes. While this series offers a more limited range of form factors (only 4 QPL case sizes, A through D, with an additional 2 case sizes (E & V) available to DSCC drawing), it does enable commercial designs / prototypes to be upgraded from commercial to COTS-Plus or even SRC9000 Space level for flight applications.

#### TBC FAMILY SIZES:

##### CWR15

TBC represents the world's smallest military approved tantalum chip capacitors technology. The case sizes are based on existing small case ceramic chip / resistor chip sizes; L, R & A case are equivalent to 0603, 0805 & 1206 sizes respectively, but with capacitance/voltage combinations significantly higher than available in 125°C rated ceramic devices. TBC represents a significant enabling technology for downsizing and reduced payload circuits for military and aerospace PCB, hybrid & flex circuit applications.


#### THH 230°C HERMETIC SERIES

Tantalum capacitor in SMD hermetic package for industrial applications like down-hole drilling, avionics and other high temperature, harsh environment application. Operational conditions 230°C/0.5xUr/1000 hrs or 200°C/0.5xUr/10000 hrs. Capacitance range 3.3-330µF, voltage range 16-63V in two case sizes, available with three optional termination designs. Manufactured using AVX patented Q process. Applying for DSCC approval.

#### TCH LOW ESR HERMETIC SERIES

Conductive Polymer in SMD hermetic package for aerospace, HighRel and other industrial applications. 10000hrs endurance at 85°C, 2000 hrs at 125°C. Capacitance range 15 - 680µF, voltage range 10-100V in two case sizes, available with three optional termination designs. Manufactured using AVX patented Q-process. Elektra award winner 2015 (product of the year). Applying for ESCC and DSCC approvals

#### THH & TCH Case Sizes





## Surface Mount Products

### PART NUMBERING, TEST & PACKAGING OPTIONS

#### Part Numbering:

AVX part numbers have 19 character fields. Standard characters are used to denote AVX series, case size, capacitance code, capacitance tolerance, voltage code and standard / Low ESR designator.

#### Test Designators:

The following table is a cross-reference between AVX and MIL designators for the various termination, test and inspection options available:

| Symbol | Parameter   | Condition                           | Designator |     |
|--------|---|-------------------------------------|------------|-----|
|        |   |                                     | MIL        | AVX |
| ^      | Termination Finish  | Hot Solder Dip                      | C          | 8   |
|        |   | Solder Fused                        | K          | 0   |
|        |   | Solder Plated                       | H          | H   |
|        |   | Gold                                | B          | 9   |
|        |   | Matte Sn                            | -          | 7   |
| #      | Lot inspection Conformance Level                          | MIL QPL (JAN brand)                 | -          | M   |
|        |   | DSCC Dwg                            | -          | D   |
|        |   | Lab/SCD/SRC9000                     | -          | L   |
|        |   | Standard                            | -          | S   |
| ++     | Surge Current Test<br>(also used for custom requirements) | No Surge                            | Z          | 00  |
|        |   | 10 Cycles Ambient                   | A          | 23  |
|        |   | 10 Cycles -55°C & +85°C             | B          | 24  |
|        |   | 10 Cycles -55°C & +85°C Pre-Weibull | C          | 45  |
| @      | Voltage Conditioning<br>(Reliability) Grade               | Non ER                              | A          | Z   |
|        |   | B Weibull                           | B          | B   |
|        |   | C Weibull                           | C          | C   |
|        |   | D Weibull                           | D          | D   |
| *      | Capacitance Tolerance                                     | ±5%                                 | J          | J   |
|        |   | ±10%                                | K          | K   |
|        |   | ±20%                                | M          | M   |
| 0      | Qualification Level                                       | 0 = N/A                             | N/A        | 0   |
|        |   | 0 = COTS-Plus or Mil 55365          | N/A        | 0   |
|        |   | T = M55365 T Level                  |            | T   |
|        |   | 4 = HRC4000 Medical                 |            | 4   |
|        |   | 5 = HRC5000 Medical                 |            | 5   |
|        |   | 6 = HRC6000 Medical                 |            | 6   |
|        |   | 9 = SRC9000 Space Level             |            | 9   |

#### Packaging Designators:


Due to the wide range of mounting processes that can be used for these products, there are many packaging options including bulk, tape / reel and waffle pack. Full dimensional information and packaging quantities are available in the packaging section (Applications Guide). Custom packaging is available for some product series (e.g. non-modular reel quantities, inverted in waffle (for wire bonding), special bar coding requirements, etc.). Please contact factory for custom requirements.

| Symbol | Parameter   | Condition              | Designator |     |
|--------|-------------|------------------------|------------|-----|
|        |             |                        | MIL        | AVX |
| □      | Bulk        | Bulk                   | Default    | B   |
|        |             | Bulk - ESD Packaging   | -          | K   |
|        | Tape & Reel | 4" Reel                | /TR4       | X   |
|        |             | 7" Reel                | /TR7       | R   |
|        |             | 13" Reel               | /TR13      | S   |
|        | Waffle Pack | Waffle Pack            | /W         | W   |
|        |             | Waffle - ESD Packaging | -          | L   |

# TAZ Series



## CWR09 - MIL-PRF-55365/4 Established Reliability, COTS-Plus & Space Level



### MARKING

(White marking on black body)



**Polarity Stripe (+)**

**Capacitance Code  
Rated Voltage**

This is the original high reliability molded tantalum chip series and the case sizes still represent the most flexible of surface mount form factors. TAZ offers nine case sizes, eight of which (A through H) are fully qualified to MIL-PRF-55365/4, and also includes the original sub-miniature R case (non-QPL).

This series is fully interchangeable with CWR06 conformal types, while offering the advantages of molded body/compliant termination construction (ensuring no TCE mismatch with any substrate). This construction is compatible with a wide range of SMT board assembly processes including wave or reflow solder, conductive epoxy or compression bonding techniques.

The parts also carry full polarity and capacitance / voltage marking. The five smaller cases are characterized by their low profile construction, with the A case being the world's smallest molded military tantalum chip.

All 4V to 50V ratings are qualified to MIL-PRF-55365 Weibull "B", "C", "D" and "T" levels, with all surge options ("A", "B" & "C") available.

For Space Level applications, AVX SRC 9000 qualification is recommended (see ratings table for part number availability).

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these are "H", "K", "C" and "B" termination, respectively, per MIL-PRF-55365). In addition, the molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.

### CASE DIMENSIONS:

millimeters (inches)

| Case Code | Length (L)<br>±0.38 (0.015)   | Width (W)<br>±0.38 (0.015)                     | Height (H)<br>±0.38 (0.015) | Term. Width (W <sub>t</sub> )           | Term. Length (A)<br>+0.25/-0.13<br>(+0.010/-0.005) | S min           | Typical Weight (g) |
|-----------|-------------------------------|--|-----------------------------|---|--|-----------------|--------------------|
| A         | 2.54 (0.100)                  | 1.27 (0.050)                                   | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 0.38<br>(0.015) | 0.016              |
| B         | 3.81 (0.150)                  | 1.27 (0.050)                                   | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 1.65<br>(0.065) | 0.025              |
| C         | 5.08 (0.200)                  | 1.27 (0.050)                                   | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 2.92<br>(0.115) | 0.035              |
| D         | 3.81 (0.150)                  | 2.54 (0.100)                                   | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 1.65<br>(0.065) | 0.045              |
| E         | 5.08 (0.200)                  | 2.54 (0.100)                                   | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 2.92<br>(0.115) | 0.065              |
| F         | 5.59 (0.220)                  | 3.43 (0.135)                                   | 1.78 (0.070)                | 3.30±0.13<br>(0.130±0.005)              | 0.76 (0.030)                                       | 3.43<br>(0.135) | 0.125              |
| G         | 6.73 (0.265)                  | 2.79 (0.110)                                   | 2.79 (0.110)                | 2.67±0.13<br>(0.105±0.005)              | 1.27 (0.050)                                       | 3.56<br>(0.140) | 0.205              |
| H         | 7.24 (0.285)                  | 3.81 (0.150)                                   | 2.79 (0.110)                | 3.68+0.13/-0.51<br>(0.145+0.005/-0.020) | 1.27 (0.050)                                       | 4.06<br>(0.160) | 0.335              |
| R         | 2.05 (0.081)<br>±0.20 (0.008) | 1.30 (0.051)<br>+0.20 (0.008)<br>-0.10 (0.004) | 1.20 (0.047)<br>max         | 1.0±0.10<br>(0.039±0.004)               | 0.50 (0.020)<br>+0.30 (0.012)<br>-0.20 (0.008)     | 0.71<br>(0.028) | 0.010              |

### CWR09 MIL-PRF-55365/4

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) at 85°C |        |         |         |         |         |         |         |
|-------------|------|--|--------|---------|---------|---------|---------|---------|---------|
| µF          | Code | 4V (C)                                     | 6V (D) | 10V (F) | 15V (H) | 20V (J) | 25V (K) | 35V (M) | 50V (N) |
| 0.10        | 104  |  |        |         |         |         |         |         | A       |
| 0.15        | 154  |  |        |         |         |         |         |         | A       |
| 0.22        | 224  |  |        |         |         |         |         | A       | B       |
| 0.33        | 334  | R  |        | R       |         | A       | A       | B       | B       |
| 0.47        | 474  |  |        | R       |         | A       | B       | B       | C       |
| 0.68        | 684  |  |        |         | A       | B       | B       | C       | D       |
| 1.0         | 105  |  |        | A/R     |         | B       | C       | D       | E       |
| 1.5         | 155  |  | A      |         | B       | C       | D       | E       | F       |
| 2.2         | 225  | A/R  |        | B       | C       | D       | E       | F       | F       |
| 3.3         | 335  |  | B      | C       | D       | E       |         | F       | G       |
| 4.7         | 475  | B  | C      | D       | E       |         | F       | G       | H       |
| 6.8         | 685  | C  | D      | E       |         | F       | G       | H       |         |
| 10          | 106  | D  | E      |         | F       |         | G       |         |         |
| 15          | 156  | E  |        | F       | G       | G       | H       |         |         |
| 22          | 226  |  | F      |         | G       | H       |         |         |         |
| 33          | 336  | F  |        | G       | H       |         |         |         |         |
| 47          | 476  |  | G      | H       |         |         |         |         |         |
| 68          | 686  | G  | H      |         |         |         |         |         |         |
| 100         | 107  | H  |        |         |         |         |         |         |         |

### HOW TO ORDER

#### COTS-PLUS & MIL QPL (CWR09):

| TAZ         | H                | 686   | *   | 006   | C  | □   | #   | @   | 0   | ^  | ++  |
|-------------|------------------|---|---|---|--|---|---|---|---|--|---|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>S = Std. Conformance<br>L = Group A<br><br>M = MIL (JAN) CWR09 | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>Z = Non-ER | <b>Qualification Level</b><br>0 = N/A<br>T = T Level<br>9 = SRC9000 | <b>Termination Finish</b><br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated<br>7 = Matte Sn (COTS-Plus only) | <b>Surge Test Option</b><br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

#### CWR09 P/N CROSS REFERENCE:

| CWR09       | D   | ^  | 686   | *   | @  | +  | □  |
|-------------|---|--|---|---|--|--|--|
| <b>Type</b> | <b>Voltage Code</b><br>C = 4Vdc<br>D = 6Vdc<br>F = 10Vdc<br>H = 15Vdc<br>J = 20Vdc<br>K = 25Vdc<br>M = 35Vdc<br>N = 50Vdc | <b>Termination Finish</b><br>H = Solder Plated<br>K = Solder Fused<br>C = Hot Solder Dipped<br>B = Gold Plated | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>T = T Level<br>A = Non-ER | <b>Surge Test Option</b><br>A = 10 cycles, +25°C<br>B = 10 cycles, -55°C & +85°C<br>C = 10 cycles, -55°C & +85°C before Weibull<br><br>If blank, None required | <b>Packaging</b><br>Bulk = Standard<br>TR = 7" T&R<br>TR13 = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. |

For RoHS compliant products, please select correct termination style.

#### SPACE LEVEL OPTIONS TO SRC9000\*:

| TAZ         | H                | 686   | *   | 006   | C  | □   | L                                      | @   | 9   | ^   | ++   |
|-------------|------------------|---|---|---|--|---|--|---|---|---|--|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>L = Group A | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf. | <b>Qualification Level</b><br>9 = SRC9000 | <b>Termination Finish</b><br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated | <b>Surge Test Option</b><br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |     |      |      |      |      |      |      |  |
|------------------------------------|---|-----|-----|------|------|------|------|------|------|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |     |      |      |      |      |      |      |  |
| Capacitance Range:                 | 0.10 µF to 100 µF   |     |     |      |      |      |      |      |      |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |     |      |      |      |      |      |      |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6   | 10   | 15   | 20   | 25   | 35   | 50   |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4   | 6.7  | 10   | 13.3 | 16.7 | 23.3 | 33.3 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 5.3 | 8   | 13.3 | 20   | 26.7 | 33.3 | 46.7 | 66.7 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 3.5 | 5.3 | 8.7  | 13.3 | 17.8 | 22.2 | 31.1 | 44.5 |  |
| Temperature Range:                 | -55°C to +125°C   |     |     |      |      |      |      |      |      |  |

# TAZ Series



## CWR09 - MIL-PRF-55365/4 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                | Parametric Specifications by Rating per MIL-PRF-55365/4 |                                     |                                    |         |       |       |        |       |       | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|--------------------------------|--------------------------------|---|-------------------------------------|------------------------------------|---------|-------|-------|--------|-------|-------|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                                |                                | Cap<br>@ 120Hz<br>µF<br>@ 25°C                          | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |       |       | DF Max |       |       | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
| CWR09 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case  | +25°C                               | +85°C                              | +125°C  | +25°C | +85°C | +125°C | +25°C | +85°C | +125°C                            | W                               | A                               | A                                | A                               | V                               | V                                | V    |
|                                | TAZ R 334 * 004 C □ # @ 0 ^ ++ |                                | R   | 0.33                                | 4                                  | 45      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.030                           | 0.03                            | 0.02                             | 0.01                            | 1.16                            | 1.05                             | 0.46 |
|                                | TAZ R 225 * 004 C □ # @ 0 ^ ++ |                                | R   | 2.2                                 | 4                                  | 12      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.030                           | 0.05                            | 0.05                             | 0.02                            | 0.60                            | 0.54                             | 0.24 |
|                                | TAZ A 225 * 004 C □ # @ 0 ^ ++ | TAZ A 225 * 004 C □ L @ 9 ^ ++ | A   | 2.2                                 | 4                                  | 8       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.63                            | 0.57                             | 0.25 |
| CWR09C^475*0+                  | TAZ B 475 * 004 C □ # @ 0 ^ ++ | TAZ B 475 * 004 C □ L @ 9 ^ ++ | B   | 4.7                                 | 4                                  | 8       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR09C^685*0+                  | TAZ C 685 * 004 C □ # @ 0 ^ ++ | TAZ C 685 * 004 C □ L @ 9 ^ ++ | C   | 6.8                                 | 4                                  | 5.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR09C^106*0+                  | TAZ D 106 * 004 C □ # @ 0 ^ ++ | TAZ D 106 * 004 C □ L @ 9 ^ ++ | D   | 10                                  | 4                                  | 4       | 1     | 10    | 12     | 8     | 8     | 10                                | 0.080                           | 0.14                            | 0.13                             | 0.06                            | 0.57                            | 0.51                             | 0.23 |
| CWR09C^156*0+                  | TAZ E 156 * 004 C □ # @ 0 ^ ++ | TAZ E 156 * 004 C □ L @ 9 ^ ++ | E   | 15                                  | 4                                  | 3.5     | 1     | 10    | 12     | 8     | 10    | 12                                | 0.090                           | 0.16                            | 0.14                             | 0.06                            | 0.56                            | 0.51                             | 0.22 |
| CWR09C^336*0+                  | TAZ F 336 * 004 C □ # @ 0 ^ ++ | TAZ F 336 * 004 C □ L @ 9 ^ ++ | F   | 33                                  | 4                                  | 2.2     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.100                           | 0.21                            | 0.19                             | 0.09                            | 0.47                            | 0.42                             | 0.19 |
| CWR09C^686*0+                  | TAZ G 686 * 004 C □ # @ 0 ^ ++ | TAZ G 686 * 004 C □ L @ 9 ^ ++ | G   | 68                                  | 4                                  | 1.1     | 3     | 30    | 36     | 10    | 12    | 12                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR09C^107*0+                  | TAZ H 107 * 004 C □ # @ 0 ^ ++ | TAZ H 107 * 004 C □ L @ 9 ^ ++ | H   | 100                                 | 4                                  | 0.9     | 4     | 40    | 48     | 10    | 12    | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR09D^155*0+                  | TAZ A 155 * 006 C □ # @ 0 ^ ++ | TAZ A 155 * 006 C □ L @ 9 ^ ++ | A   | 1.5                                 | 6                                  | 8       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.63                            | 0.57                             | 0.25 |
| CWR09D^335*0+                  | TAZ B 335 * 006 C □ # @ 0 ^ ++ | TAZ B 335 * 006 C □ L @ 9 ^ ++ | B   | 3.3                                 | 6                                  | 8       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR09D^475*0+                  | TAZ C 475 * 006 C □ # @ 0 ^ ++ | TAZ C 475 * 006 C □ L @ 9 ^ ++ | C   | 4.7                                 | 6                                  | 5.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR09D^685*0+                  | TAZ D 685 * 006 C □ # @ 0 ^ ++ | TAZ D 685 * 006 C □ L @ 9 ^ ++ | D   | 6.8                                 | 6                                  | 4.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.13                            | 0.12                             | 0.05                            | 0.60                            | 0.54                             | 0.24 |
| CWR09D^106*0+                  | TAZ E 106 * 006 C □ # @ 0 ^ ++ | TAZ E 106 * 006 C □ L @ 9 ^ ++ | E   | 10                                  | 6                                  | 3.5     | 1     | 10    | 12     | 8     | 10    | 12                                | 0.090                           | 0.16                            | 0.14                             | 0.06                            | 0.56                            | 0.51                             | 0.22 |
| CWR09D^226*0+                  | TAZ F 226 * 006 C □ # @ 0 ^ ++ | TAZ F 226 * 006 C □ L @ 9 ^ ++ | F   | 22                                  | 6                                  | 2.2     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.100                           | 0.21                            | 0.19                             | 0.09                            | 0.47                            | 0.42                             | 0.19 |
| CWR09D^476*0+                  | TAZ G 476 * 006 C □ # @ 0 ^ ++ | TAZ G 476 * 006 C □ L @ 9 ^ ++ | G   | 47                                  | 6                                  | 1.1     | 3     | 30    | 36     | 10    | 12    | 12                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR09D^686*0+                  | TAZ H 686 * 006 C □ # @ 0 ^ ++ | TAZ H 686 * 006 C □ L @ 9 ^ ++ | H   | 68                                  | 6                                  | 0.9     | 4     | 40    | 48     | 10    | 12    | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
|                                | TAZ R 334 * 010 C □ # @ 0 ^ ++ |                                | R   | 0.33                                | 10                                 | 50      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.030                           | 0.02                            | 0.02                             | 0.01                            | 1.22                            | 1.10                             | 0.49 |
|                                | TAZ R 474 * 010 C □ # @ 0 ^ ++ |                                | R   | 0.47                                | 10                                 | 50      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.030                           | 0.02                            | 0.02                             | 0.01                            | 1.22                            | 1.10                             | 0.49 |
|                                | TAZ R 105 * 010 C □ # @ 0 ^ ++ |                                | R   | 1                                   | 10                                 | 10      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.030                           | 0.05                            | 0.05                             | 0.02                            | 0.55                            | 0.49                             | 0.22 |
| CWR09F^105*0+                  | TAZ A 105 * 010 C □ # @ 0 ^ ++ | TAZ A 105 * 010 C □ L @ 9 ^ ++ | A   | 1                                   | 10                                 | 10      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.07                            | 0.06                             | 0.03                            | 0.71                            | 0.64                             | 0.28 |
| CWR09F^225*0+                  | TAZ B 225 * 010 C □ # @ 0 ^ ++ | TAZ B 225 * 010 C □ L @ 9 ^ ++ | B   | 2.2                                 | 10                                 | 8       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR09F^335*0+                  | TAZ C 335 * 010 C □ # @ 0 ^ ++ | TAZ C 335 * 010 C □ L @ 9 ^ ++ | C   | 3.3                                 | 10                                 | 5.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR09F^475*0+                  | TAZ D 475 * 010 C □ # @ 0 ^ ++ | TAZ D 475 * 010 C □ L @ 9 ^ ++ | D   | 4.7                                 | 10                                 | 4.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.13                            | 0.12                             | 0.05                            | 0.60                            | 0.54                             | 0.24 |
| CWR09F^685*0+                  | TAZ E 685 * 010 C □ # @ 0 ^ ++ | TAZ E 685 * 010 C □ L @ 9 ^ ++ | E   | 6.8                                 | 10                                 | 3.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.090                           | 0.16                            | 0.14                             | 0.06                            | 0.56                            | 0.51                             | 0.22 |
| CWR09F^156*0+                  | TAZ F 156 * 010 C □ # @ 0 ^ ++ | TAZ F 156 * 010 C □ L @ 9 ^ ++ | F   | 15                                  | 10                                 | 2.5     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.100                           | 0.20                            | 0.18                             | 0.08                            | 0.50                            | 0.45                             | 0.20 |
| CWR09F^336*0+                  | TAZ G 336 * 010 C □ # @ 0 ^ ++ | TAZ G 336 * 010 C □ L @ 9 ^ ++ | G   | 33                                  | 10                                 | 1.1     | 3     | 30    | 36     | 10    | 12    | 12                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR09F^476*0+                  | TAZ H 476 * 010 C □ # @ 0 ^ ++ | TAZ H 476 * 010 C □ L @ 9 ^ ++ | H   | 47                                  | 10                                 | 0.9     | 5     | 50    | 60     | 10    | 12    | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR09H^684*0+                  | TAZ A 684 * 015 C □ # @ 0 ^ ++ | TAZ A 684 * 015 C □ L @ 9 ^ ++ | A   | 0.68                                | 15                                 | 12      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR09H^155*0+                  | TAZ B 155 * 015 C □ # @ 0 ^ ++ | TAZ B 155 * 015 C □ L @ 9 ^ ++ | B   | 1.5                                 | 15                                 | 8       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR09H^225*0+                  | TAZ C 225 * 015 C □ # @ 0 ^ ++ | TAZ C 225 * 015 C □ L @ 9 ^ ++ | C   | 2.2                                 | 15                                 | 5.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR09H^335*0+                  | TAZ D 335 * 015 C □ # @ 0 ^ ++ | TAZ D 335 * 015 C □ L @ 9 ^ ++ | D   | 3.3                                 | 15                                 | 5       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.13                            | 0.11                             | 0.05                            | 0.63                            | 0.57                             | 0.25 |
| CWR09H^475*0+                  | TAZ E 475 * 015 C □ # @ 0 ^ ++ | TAZ E 475 * 015 C □ L @ 9 ^ ++ | E   | 4.7                                 | 15                                 | 4       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.090                           | 0.15                            | 0.14                             | 0.06                            | 0.60                            | 0.54                             | 0.24 |
| CWR09H^106*0+                  | TAZ F 106 * 015 C □ # @ 0 ^ ++ | TAZ F 106 * 015 C □ L @ 9 ^ ++ | F   | 10                                  | 15                                 | 2.5     | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.100                           | 0.20                            | 0.18                             | 0.08                            | 0.50                            | 0.45                             | 0.20 |
| CWR09H^226*0+                  | TAZ G 226 * 015 C □ # @ 0 ^ ++ | TAZ G 226 * 015 C □ L @ 9 ^ ++ | G   | 22                                  | 15                                 | 1.1     | 4     | 40    | 48     | 6     | 8     | 8                                 | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR09H^336*0+                  | TAZ H 336 * 015 C □ # @ 0 ^ ++ | TAZ H 336 * 015 C □ L @ 9 ^ ++ | H   | 33                                  | 15                                 | 0.9     | 5     | 50    | 60     | 8     | 10    | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR09J^474*0+                  | TAZ A 474 * 020 C □ # @ 0 ^ ++ | TAZ A 474 * 020 C □ L @ 9 ^ ++ | A   | 0.47                                | 20                                 | 14      | 1     | 10    | 12     | 8     | 8     | 10                                | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.84                            | 0.75                             | 0.33 |
| CWR09J^684*0+                  | TAZ B 684 * 020 C □ # @ 0 ^ ++ | TAZ B 684 * 020 C □ L @ 9 ^ ++ | B   | 0.68                                | 20                                 | 10      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.08                            | 0.08                             | 0.03                            | 0.84                            | 0.75                             | 0.33 |
| CWR09J^105*0+                  | TAZ B 105 * 020 C □ # @ 0 ^ ++ | TAZ B 105 * 020 C □ L @ 9 ^ ++ | B   | 1                                   | 20                                 | 12      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.08                            | 0.07                             | 0.03                            | 0.92                            | 0.82                             | 0.37 |
| CWR09J^155*0+                  | TAZ C 155 * 020 C □ # @ 0 ^ ++ | TAZ C 155 * 020 C □ L @ 9 ^ ++ | C   | 1.5                                 | 20                                 | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.11                            | 0.10                             | 0.04                            | 0.67                            | 0.60                             | 0.27 |
| CWR09J^225*0+                  | TAZ D 225 * 020 C □ # @ 0 ^ ++ | TAZ D 225 * 020 C □ L @ 9 ^ ++ | D   | 2.2                                 | 20                                 | 5       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.13                            | 0.11                             | 0.05                            | 0.63                            | 0.57                             | 0.25 |
| CWR09J^335*0+                  | TAZ E 335 * 020 C □ # @ 0 ^ ++ | TAZ E 335 * 020 C □ L @ 9 ^ ++ | E   | 3.3                                 | 20                                 | 4       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.090                           | 0.15                            | 0.14                             | 0.06                            | 0.60                            | 0.54                             | 0.24 |
| CWR09J^685*0+                  | TAZ F 685 * 020 C □ # @ 0 ^ ++ | TAZ F 685 * 020 C □ L @ 9 ^ ++ | F   | 6.8                                 | 20                                 | 2.4     | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.100                           | 0.20                            | 0.18                             | 0.08                            | 0.49                            | 0.44                             | 0.20 |
| CWR09J^156*0+                  | TAZ G 156 * 020 C □ # @ 0 ^ ++ | TAZ G 156 * 020 C □ L @ 9 ^ ++ | G   | 15                                  | 20                                 | 1.1     | 3     | 30    | 36     | 6     | 8     | 8                                 | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR09J^226*0+                  | TAZ H 226 * 020 C □ # @ 0 ^ ++ | TAZ H 226 * 020 C □ L @ 9 ^ ++ | H   | 22                                  | 20                                 | 0.9     | 4     | 40    | 48     | 6     | 8     | 8                                 | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR09K^334*0+                  | TAZ A 334 * 025 C □ # @ 0 ^ ++ | TAZ A 334 * 025 C □ L @ 9 ^ ++ | A   | 0.33                                | 25                                 | 15      | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.87                            | 0.78                             | 0.35 |
| CWR09K^684*0+                  | TAZ B 684 * 025 C □ # @ 0 ^ ++ | TAZ B 684 * 025 C □ L @ 9 ^ ++ | B   | 0.68                                | 25                                 | 7.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.10                            | 0.09                             | 0.04                            | 0.72                            | 0.65                             | 0.29 |
| CWR09K^105*0+                  | TAZ C 105 * 025 C □ # @ 0 ^ ++ | TAZ C 105 * 025 C □ L @ 9 ^ ++ | C   | 1                                   | 25                                 | 6.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.11                            | 0.10                             | 0.04                            | 0.70                            | 0.63                             | 0.28 |
| CWR09K^155*0+                  | TAZ D 155 * 025 C □ # @ 0 ^ ++ | TAZ D 155 * 025 C □ L @ 9 ^ ++ | D   | 1.5                                 | 25                                 | 6.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.11                            | 0.10                             | 0.04                            | 0.72                            | 0.65                             | 0.29 |
| CWR09K^225*0+                  | TAZ E 225 * 025 C □ # @ 0 ^ ++ | TAZ E 225 * 025 C □ L @ 9 ^ ++ | E   | 2.2                                 | 25                                 | 3.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.090                           | 0.16                            | 0.14                             | 0.06                            | 0.56                            | 0.51                             | 0.22 |
| CWR09K^475*0+                  | TAZ F 475 * 025 C □ # @ 0 ^ ++ | TAZ F 475 * 025 C □ L @ 9 ^ ++ | F   | 4.7                                 | 25                                 | 2.5     | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.100                           | 0.20                            | 0.18                             | 0.08                            | 0.50                            | 0.45                             | 0.20 |
| CWR09K^685*0+                  | TAZ G 685 * 025 C □ # @ 0 ^ ++ | TAZ G 685 * 025 C □ L @ 9 ^ ++ | G   | 6.8                                 | 25                                 | 1.2     | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.125                           | 0.32                            | 0.29                             | 0.13                            | 0.39                            | 0.35                             | 0.15 |
| CWR09K^106*0+                  | TAZ G 106 * 025 C □ # @ 0 ^ ++ | TAZ G 106 * 025 C □ L @ 9 ^ ++ | G   | 10                                  | 25                                 | 1.4     | 3     | 30    |        |       |       |                                   |                                 |                                 |                                  |                                 |                                 |                                  |      |

# TAZ Series



## CWR09 - MIL-PRF-55365/4 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                | Parametric Specifications by Rating per MIL-PRF-55365/4 |                                     |                                    |               |               |                |              |                    |              | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|--------------------------------|--------------------------------|---|-------------------------------------|------------------------------------|---------------|---------------|----------------|--------------|--------------------|--------------|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                                |                                | Cap<br>@ 120Hz<br>µF<br>@ 25°C                          | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max       |               |                | DF Max       |                    |              | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
|                                |                                |                                |   |                                     |                                    | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +(85/125)°C<br>(%) | -55°C<br>(%) |                                   |                                 |                                 |                                  |                                 |                                 |                                  |      |
| CWR09M^224*0+                  | TAZ A 224 * 035 C □ # @ 0 ^ ++ | TAZ A 224 * 035 C □ L @ 9 ^ ++ | A   | 0.22                                | 35                                 | 18            | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.050                           | 0.05                            | 0.05                             | 0.02                            | 0.95                            | 0.85                             | 0.38 |
| CWR09M^474*0+                  | TAZ B 474 * 035 C □ # @ 0 ^ ++ | TAZ B 474 * 035 C □ L @ 9 ^ ++ | B   | 0.47                                | 35                                 | 10            | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.070                           | 0.08                            | 0.08                             | 0.03                            | 0.84                            | 0.75                             | 0.33 |
| CWR09M^684*0+                  | TAZ C 684 * 035 C □ # @ 0 ^ ++ | TAZ C 684 * 035 C □ L @ 9 ^ ++ | C   | 0.68                                | 35                                 | 8             | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR09M^105*0+                  | TAZ D 105 * 035 C □ # @ 0 ^ ++ | TAZ D 105 * 035 C □ L @ 9 ^ ++ | D   | 1                                   | 35                                 | 6.5           | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.080                           | 0.11                            | 0.10                             | 0.04                            | 0.72                            | 0.65                             | 0.29 |
| CWR09M^155*0+                  | TAZ E 155 * 035 C □ # @ 0 ^ ++ | TAZ E 155 * 035 C □ L @ 9 ^ ++ | E   | 1.5                                 | 35                                 | 4.5           | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.090                           | 0.14                            | 0.13                             | 0.06                            | 0.64                            | 0.57                             | 0.25 |
| CWR09M^335*0+                  | TAZ F 335 * 035 C □ # @ 0 ^ ++ | TAZ F 335 * 035 C □ L @ 9 ^ ++ | F   | 3.3                                 | 35                                 | 2.5           | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.100                           | 0.20                            | 0.18                             | 0.08                            | 0.50                            | 0.45                             | 0.20 |
| CWR09M^475*0+                  | TAZ G 475 * 035 C □ # @ 0 ^ ++ | TAZ G 475 * 035 C □ L @ 9 ^ ++ | G   | 4.7                                 | 35                                 | 1.5           | 2             | 20             | 24           | 6                  | 8            | 8                                 | 0.125                           | 0.29                            | 0.26                             | 0.12                            | 0.43                            | 0.39                             | 0.17 |
| CWR09M^685*0+                  | TAZ H 685 * 035 C □ # @ 0 ^ ++ | TAZ H 685 * 035 C □ L @ 9 ^ ++ | H   | 6.8                                 | 35                                 | 1.3           | 3             | 30             | 36           | 6                  | 8            | 8                                 | 0.150                           | 0.34                            | 0.31                             | 0.14                            | 0.44                            | 0.40                             | 0.18 |
| CWR09N^104*0+                  | TAZ A 104 * 050 C □ # @ 0 ^ ++ | TAZ A 104 * 050 C □ L @ 9 ^ ++ | A   | 0.1                                 | 50                                 | 22            | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.050                           | 0.05                            | 0.04                             | 0.02                            | 1.05                            | 0.94                             | 0.42 |
| CWR09N^154*0+                  | TAZ A 154 * 050 C □ # @ 0 ^ ++ | TAZ A 154 * 050 C □ L @ 9 ^ ++ | A   | 0.15                                | 50                                 | 17            | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.050                           | 0.05                            | 0.05                             | 0.02                            | 0.92                            | 0.83                             | 0.37 |
| CWR09N^224*0+                  | TAZ B 224 * 050 C □ # @ 0 ^ ++ | TAZ B 224 * 050 C □ L @ 9 ^ ++ | B   | 0.22                                | 50                                 | 14            | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.070                           | 0.07                            | 0.06                             | 0.03                            | 0.99                            | 0.89                             | 0.40 |
| CWR09N^334*0+                  | TAZ B 334 * 050 C □ # @ 0 ^ ++ | TAZ B 334 * 050 C □ L @ 9 ^ ++ | B   | 0.33                                | 50                                 | 12            | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.070                           | 0.08                            | 0.07                             | 0.03                            | 0.92                            | 0.82                             | 0.37 |
| CWR09N^474*0+                  | TAZ C 474 * 050 C □ # @ 0 ^ ++ | TAZ C 474 * 050 C □ L @ 9 ^ ++ | C   | 0.47                                | 50                                 | 8             | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR09N^684*0+                  | TAZ D 684 * 050 C □ # @ 0 ^ ++ | TAZ D 684 * 050 C □ L @ 9 ^ ++ | D   | 0.68                                | 50                                 | 7             | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.080                           | 0.11                            | 0.10                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR09N^105*0+                  | TAZ E 105 * 050 C □ # @ 0 ^ ++ | TAZ E 105 * 050 C □ L @ 9 ^ ++ | E   | 1                                   | 50                                 | 6             | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.090                           | 0.12                            | 0.11                             | 0.05                            | 0.73                            | 0.66                             | 0.29 |
| CWR09N^155*0+                  | TAZ F 155 * 050 C □ # @ 0 ^ ++ | TAZ F 155 * 050 C □ L @ 9 ^ ++ | F   | 1.5                                 | 50                                 | 4             | 1             | 10             | 12           | 6                  | 8            | 8                                 | 0.100                           | 0.16                            | 0.14                             | 0.06                            | 0.63                            | 0.57                             | 0.25 |
| CWR09N^225*0+                  | TAZ F 225 * 050 C □ # @ 0 ^ ++ | TAZ F 225 * 050 C □ L @ 9 ^ ++ | F   | 2.2                                 | 50                                 | 2.5           | 2             | 20             | 24           | 6                  | 8            | 8                                 | 0.100                           | 0.20                            | 0.18                             | 0.08                            | 0.50                            | 0.45                             | 0.20 |
| CWR09N^335*0+                  | TAZ G 335 * 050 C □ # @ 0 ^ ++ | TAZ G 335 * 050 C □ L @ 9 ^ ++ | G   | 3.3                                 | 50                                 | 2             | 2             | 20             | 24           | 6                  | 8            | 8                                 | 0.125                           | 0.25                            | 0.23                             | 0.10                            | 0.50                            | 0.45                             | 0.20 |
| CWR09N^475*0+                  | TAZ H 475 * 050 C □ # @ 0 ^ ++ | TAZ H 475 * 050 C □ L @ 9 ^ ++ | H   | 4.7                                 | 50                                 | 1.5           | 3             | 30             | 36           | 6                  | 8            | 8                                 | 0.150                           | 0.32                            | 0.28                             | 0.13                            | 0.47                            | 0.43                             | 0.19 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# TAZ Series



## CWR19 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level



An extended range of capacitor ratings beyond CWR09 that is fully qualified to MIL-PRF-55365/11, this series represents the most flexible of surface mount form factors, offering nine case sizes (the original A through H of CWR09) and adds the new X case size.

The molded body / compliant termination construction ensures no TCE mismatch with any substrate. This construction is compatible with a wide range of SMT board assembly processes including wave or reflow solder, conductive epoxy or compression bonding techniques. The parts also carry full polarity and capacitance / voltage marking.


The four smaller cases are characterized by their low profile construction, with the A case being the world's smallest molded military tantalum chip.

The series is qualified to MIL-PRF-55365 Weibull "B", "C", "D" and "T" levels, with all surge options ("A", "B" & "C") available.

For Space Level applications, AVX SRC 9000 qualification is recommended (see ratings table for part number availability).

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these are "H", "K", "C" and "B" termination, respectively, per MIL-PRF-55365). In addition, the molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.



### MARKING

(White marking on black body)



**Polarity Stripe (+)**

**Capacitance Code**  
**Rated Voltage**

### CASE DIMENSIONS:

millimeters (inches)

| Case Code | Length (L)<br>±0.38 (0.015) | Width (W)<br>±0.38 (0.015) | Height (H)<br>±0.38 (0.015) | Term. Width (W <sub>t</sub> )           | Term. Length (A)<br>+0.25/-0.13<br>(+0.010/-0.005) | S min        | Typical Weight (g) |
|-----------|-----------------------------|----------------------------|-----------------------------|---|--|--------------|--------------------|
| A         | 2.54 (0.100)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 0.38 (0.015) | 0.016              |
| B         | 3.81 (0.150)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 1.65 (0.065) | 0.025              |
| C         | 5.08 (0.200)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 2.92 (0.115) | 0.035              |
| D         | 3.81 (0.150)                | 2.54 (0.100)               | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 1.65 (0.065) | 0.045              |
| E         | 5.08 (0.200)                | 2.54 (0.100)               | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 2.92 (0.115) | 0.065              |
| F         | 5.59 (0.220)                | 3.43 (0.135)               | 1.78 (0.070)                | 3.30±0.13<br>(0.130±0.005)              | 0.76 (0.030)                                       | 3.43 (0.135) | 0.125              |
| G         | 6.73 (0.265)                | 2.79 (0.110)               | 2.79 (0.110)                | 2.67±0.13<br>(0.105±0.005)              | 1.27 (0.050)                                       | 3.56 (0.140) | 0.205              |
| H         | 7.24 (0.285)                | 3.81 (0.150)               | 2.79 (0.110)                | 3.68+0.13/-0.51<br>(0.145+0.005/-0.020) | 1.27 (0.050)                                       | 4.06 (0.160) | 0.335              |
| X         | 6.93 (0.273)                | 5.41 (0.213)               | 2.74 (0.108)                | 3.05±0.13<br>(0.120±0.005)              | 1.19 (0.047)                                       | N/A          | 0.420              |

### CWR19-MIL-PRF 55365/11

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated voltage DC (V <sub>R</sub> ) at 85°C |        |         |         |         |         |         |
|-------------|------|--|--------|---------|---------|---------|---------|---------|
| µF          | Code | 4V (C)                                     | 6V (D) | 10V (F) | 15V (H) | 20V (J) | 25V (K) | 35V (M) |
| 0.33        | 334  |  |        |         |         |         |         | A       |
| 0.47        | 474  |  |        |         |         |         | A       |         |
| 0.68        | 684  |  |        |         |         |         | A       |         |
| 1.0         | 105  |  |        |         | A       | A       | B       |         |
| 1.5         | 155  |  |        |         | A       | B       |         |         |
| 2.2         | 225  |  |        | A       | A       | B       | D       |         |
| 3.3         | 335  | A  | A      | A       | B       | D       | E       |         |
| 4.7         | 475  | A  | A      | B/C     | B/C/D   | E       |         |         |
| 6.8         | 685  | A  | B      | B/C/D   | D/E     | E       | F       | G       |
| 10          | 106  | B  | B      | B/C/D/E | D/E     | E/F     |         | H       |
| 15          | 156  | B  | B/D/E  | D/E     | E/F     | F       | G       | X       |
| 22          | 226  | B/D  | D/E    | E       | F       | G       | G/H     |         |
| 33          | 336  | D/E  | E      | F       | F/G     | H       | H       |         |
| 47          | 476  | E  | F      | F/G     | G/H     | H/X     |         |         |
| 68          | 686  | E  | F/G    | G       | G/H     |         |         |         |
| 100         | 107  | F  | G      | G/H     | H       |         |         |         |
| 150         | 157  | G  | G      | H/X     |         |         |         |         |
| 220         | 227  | H  | H      | H       |         |         |         |         |
| 330         | 337  | H  | H      |         |         |         |         |         |



### HOW TO ORDER

#### COTS-PLUS & MIL QPL (CWR19):

| TAZ  | H         | 227  | *  | 006   | C   | □  | #  | @  | 0  | ^   | ++   |
|------|-----------|--|--|---|---|--|--|--|--|---|--|
| Type | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>M = ±20%<br>K = ±10%<br>J = ±5% | Voltage Code<br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc | Standard or Low ESR Range<br>C = Std ESR<br>L = Low ESR | Packaging<br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | Inspection Level<br>S = Std. Conformance<br>L = Group A<br><br>M = MIL (JAN) CWR19 | Reliability Grade<br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>Z = Non-ER | Qualification Level<br>0 = N/A<br>T = T Level<br>9 = SRC9000 | Termination Finish<br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated<br>7 = Matte Sn (COTS-Plus only) | Surge Test Option<br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |

#### CWR19 P/N CROSS REFERENCE:

| CWR19 | D   | ^   | 227  | *  | @   | H         | +   | □   |
|-------|---|---|--|--|---|-----------|---|---|
| Type  | Voltage Code<br>C = 4Vdc<br>D = 6Vdc<br>F = 10Vdc<br>H = 15Vdc<br>J = 20Vdc<br>K = 25Vdc<br>M = 35Vdc | Termination Finish<br>H = Solder Plated<br>K = Solder Fused<br>C = Hot Solder Dipped<br>B = Gold Plated | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>M = ±20%<br>K = ±10%<br>J = ±5% | Reliability Grade<br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>T = T Level<br>A = Non-ER | Case Size | Surge Test Option<br>A = 10 cycles, +25°C<br>B = 10 cycles, -55°C & +85°C<br>C = 10 cycles, -55°C & +85°C before Weibull<br>Z = None required | Packaging<br>Bulk = Standard<br>T&R = 7" T&R<br>T&R13 = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. |

#### SPACE LEVEL OPTIONS TO SRC9000\*:

| TAZ  | H         | 227  | *  | 006   | C   | □  | L                               | @  | 9                                  | ^  | ++  |
|------|-----------|--|--|---|---|--|---------------------------------|--|------------------------------------|--|---|
| Type | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>M = ±20%<br>K = ±10%<br>J = ±5% | Voltage Code<br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc | Standard or Low ESR Range<br>C = Std ESR<br>L = Low ESR | Packaging<br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | Inspection Level<br>L = Group A | Reliability Grade<br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf. | Qualification Level<br>9 = SRC9000 | Termination Finish<br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated | Surge Test Option<br>45 = 10 cycles, -55°C & +85°C before Weibull |

\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |     |      |      |      |      |      |  |
|------------------------------------|---|-----|-----|------|------|------|------|------|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |     |      |      |      |      |      |  |
| Capacitance Range:                 | 0.33 µF to 330 µF   |     |     |      |      |      |      |      |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |     |      |      |      |      |      |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6   | 10   | 15   | 20   | 25   | 35   |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4   | 6.7  | 10   | 13.3 | 16.7 | 23.3 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 5.3 | 8   | 13.3 | 20   | 26.7 | 33.3 | 46.7 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 3.5 | 5.3 | 8.7  | 13.3 | 17.8 | 22.2 | 31.1 |  |
| Temperature Range:                 | -55°C to +125°C   |     |     |      |      |      |      |      |  |

# TAZ Series



## CWR19 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                | Parametric Specifications by Rating per MIL-PRF-55365/11 |                                     |                                    |         |               |               |                |              |                  | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|--------------------------------|--------------------------------|--|-------------------------------------|------------------------------------|---------|---------------|---------------|----------------|--------------|------------------|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                                |                                | Cap<br>@ 120Hz<br>μF<br>@ 25°C                           | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |               |               | DF Max         |              |                  | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
| CWR19 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case   | μF                                  | V                                  | Ohms    | +25°C<br>(μA) | +85°C<br>(μA) | +125°C<br>(μA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%)                      | W                               | A                               | A                                | A                               | V                               | V                                | V    |
| CWR19C^335^@A+□                | TAZ A 335 * 004 C □ # @ 0 ^ ++ | TAZ A 335 * 004 C □ L @ 9 ^ ++ | A  | 3.3                                 | 4                                  | 12      | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR19C^475^@A+□                | TAZ A 475 * 004 C □ # @ 0 ^ ++ | TAZ A 475 * 004 C □ L @ 9 ^ ++ | A  | 4.7                                 | 4                                  | 12      | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR19C^685^@A+□                | TAZ A 685 * 004 C □ # @ 0 ^ ++ | TAZ A 685 * 004 C □ L @ 9 ^ ++ | A  | 6.8                                 | 4                                  | 12      | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR19C^106^@B+□                | TAZ B 106 * 004 C □ # @ 0 ^ ++ | TAZ B 106 * 004 C □ L @ 9 ^ ++ | B  | 10                                  | 4                                  | 8       | 1             | 10            | 12             | 8            | 10               | 10                                | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19C^156^@B+□                | TAZ B 156 * 004 C □ # @ 0 ^ ++ | TAZ B 156 * 004 C □ L @ 9 ^ ++ | B  | 15                                  | 4                                  | 8       | 1             | 10            | 12             | 8            | 10               | 10                                | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19C^226^@B+□                | TAZ B 226 * 004 C □ # @ 0 ^ ++ | TAZ B 226 * 004 C □ L @ 9 ^ ++ | B  | 22                                  | 4                                  | 8       | 1             | 10            | 12             | 8            | 10               | 10                                | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19C^226^@D+□                | TAZ D 226 * 004 C □ # @ 0 ^ ++ | TAZ D 226 * 004 C □ L @ 9 ^ ++ | D  | 22                                  | 4                                  | 4       | 1             | 10            | 12             | 8            | 10               | 12                                | 0.080                           | 0.14                            | 0.13                             | 0.06                            | 0.57                            | 0.51                             | 0.23 |
| CWR19C^336^@D+□                | TAZ D 336 * 004 C □ # @ 0 ^ ++ | TAZ D 336 * 004 C □ L @ 9 ^ ++ | D  | 33                                  | 4                                  | 4       | 2             | 20            | 24             | 8            | 10               | 12                                | 0.080                           | 0.14                            | 0.13                             | 0.06                            | 0.57                            | 0.51                             | 0.23 |
| CWR19C^336^@E+□                | TAZ E 336 * 004 C □ # @ 0 ^ ++ | TAZ E 336 * 004 C □ L @ 9 ^ ++ | E  | 33                                  | 4                                  | 3       | 2             | 20            | 24             | 8            | 10               | 12                                | 0.090                           | 0.17                            | 0.16                             | 0.07                            | 0.52                            | 0.47                             | 0.21 |
| CWR19C^476^@E+□                | TAZ E 476 * 004 C □ # @ 0 ^ ++ | TAZ E 476 * 004 C □ L @ 9 ^ ++ | E  | 47                                  | 4                                  | 3       | 2             | 20            | 24             | 8            | 10               | 12                                | 0.090                           | 0.17                            | 0.16                             | 0.07                            | 0.52                            | 0.47                             | 0.21 |
| CWR19C^686^@E+□                | TAZ E 686 * 004 C □ # @ 0 ^ ++ | TAZ E 686 * 004 C □ L @ 9 ^ ++ | E  | 68                                  | 4                                  | 3       | 3             | 30            | 36             | 8            | 10               | 12                                | 0.090                           | 0.17                            | 0.16                             | 0.07                            | 0.52                            | 0.47                             | 0.21 |
| CWR19C^107^@F+□                | TAZ F 107 * 004 C □ # @ 0 ^ ++ | TAZ F 107 * 004 C □ L @ 9 ^ ++ | F  | 100                                 | 4                                  | 2       | 4             | 40            | 48             | 10           | 12               | 12                                | 0.100                           | 0.22                            | 0.20                             | 0.09                            | 0.45                            | 0.40                             | 0.18 |
| CWR19C^157^@G+□                | TAZ G 157 * 004 C □ # @ 0 ^ ++ | TAZ G 157 * 004 C □ L @ 9 ^ ++ | G  | 150                                 | 4                                  | 1       | 6             | 60            | 72             | 10           | 12               | 12                                | 0.125                           | 0.35                            | 0.32                             | 0.14                            | 0.35                            | 0.32                             | 0.14 |
| CWR19C^227^@H+□                | TAZ H 227 * 004 C □ # @ 0 ^ ++ | TAZ H 227 * 004 C □ L @ 9 ^ ++ | H  | 220                                 | 4                                  | 1       | 8             | 80            | 96             | 10           | 12               | 12                                | 0.150                           | 0.39                            | 0.35                             | 0.15                            | 0.39                            | 0.35                             | 0.15 |
| CWR19C^337^@H+□                | TAZ H 337 * 004 C □ # @ 0 ^ ++ | TAZ H 337 * 004 C □ L @ 9 ^ ++ | H  | 330                                 | 4                                  | 0.9     | 10            | 100           | 120            | 10           | 12               | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19D^335^@A+□                | TAZ A 335 * 006 C □ # @ 0 ^ ++ | TAZ A 335 * 006 C □ L @ 9 ^ ++ | A  | 3.3                                 | 6                                  | 12      | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR19D^475^@A+□                | TAZ A 475 * 006 C □ # @ 0 ^ ++ | TAZ A 475 * 006 C □ L @ 9 ^ ++ | A  | 4.7                                 | 6                                  | 12      | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR19D^685^@B+□                | TAZ B 685 * 006 C □ # @ 0 ^ ++ | TAZ B 685 * 006 C □ L @ 9 ^ ++ | B  | 6.8                                 | 6                                  | 8       | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19D^106^@B+□                | TAZ B 106 * 006 C □ # @ 0 ^ ++ | TAZ B 106 * 006 C □ L @ 9 ^ ++ | B  | 10                                  | 6                                  | 8       | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19D^156^@B+□                | TAZ B 156 * 006 C □ # @ 0 ^ ++ | TAZ B 156 * 006 C □ L @ 9 ^ ++ | B  | 15                                  | 6                                  | 8       | 1             | 10            | 12             | 8            | 10               | 10                                | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19D^156^@D+□                | TAZ D 156 * 006 C □ # @ 0 ^ ++ | TAZ D 156 * 006 C □ L @ 9 ^ ++ | D  | 15                                  | 6                                  | 5       | 1             | 10            | 12             | 8            | 10               | 12                                | 0.080                           | 0.13                            | 0.11                             | 0.05                            | 0.63                            | 0.57                             | 0.25 |
| CWR19D^226^@D+□                | TAZ D 226 * 006 C □ # @ 0 ^ ++ | TAZ D 226 * 006 C □ L @ 9 ^ ++ | D  | 22                                  | 6                                  | 5       | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.080                           | 0.13                            | 0.11                             | 0.05                            | 0.63                            | 0.57                             | 0.25 |
| CWR19D^156^@E+□                | TAZ E 156 * 006 C □ # @ 0 ^ ++ | TAZ E 156 * 006 C □ L @ 9 ^ ++ | E  | 15                                  | 6                                  | 3       | 1             | 10            | 12             | 8            | 10               | 12                                | 0.090                           | 0.17                            | 0.16                             | 0.07                            | 0.52                            | 0.47                             | 0.21 |
| CWR19D^226^@E+□                | TAZ E 226 * 006 C □ # @ 0 ^ ++ | TAZ E 226 * 006 C □ L @ 9 ^ ++ | E  | 22                                  | 6                                  | 3.5     | 2             | 20            | 24             | 8            | 10               | 12                                | 0.090                           | 0.16                            | 0.14                             | 0.06                            | 0.56                            | 0.51                             | 0.22 |
| CWR19D^336^@E+□                | TAZ E 336 * 006 C □ # @ 0 ^ ++ | TAZ E 336 * 006 C □ L @ 9 ^ ++ | E  | 33                                  | 6                                  | 3.5     | 2             | 20            | 24             | 6            | 8                | 8                                 | 0.090                           | 0.16                            | 0.14                             | 0.06                            | 0.56                            | 0.51                             | 0.22 |
| CWR19D^476^@F+□                | TAZ F 476 * 006 C □ # @ 0 ^ ++ | TAZ F 476 * 006 C □ L @ 9 ^ ++ | F  | 47                                  | 6                                  | 3.5     | 3             | 30            | 36             | 8            | 10               | 12                                | 0.100                           | 0.17                            | 0.15                             | 0.07                            | 0.59                            | 0.53                             | 0.24 |
| CWR19D^686^@F+□                | TAZ F 686 * 006 C □ # @ 0 ^ ++ | TAZ F 686 * 006 C □ L @ 9 ^ ++ | F  | 68                                  | 6                                  | 1.5     | 4             | 40            | 48             | 10           | 12               | 12                                | 0.100                           | 0.26                            | 0.23                             | 0.10                            | 0.39                            | 0.35                             | 0.15 |
| CWR19D^686^@G+□                | TAZ G 686 * 006 C □ # @ 0 ^ ++ | TAZ G 686 * 006 C □ L @ 9 ^ ++ | G  | 68                                  | 6                                  | 1       | 4             | 40            | 48             | 10           | 12               | 12                                | 0.125                           | 0.35                            | 0.32                             | 0.14                            | 0.35                            | 0.32                             | 0.14 |
| CWR19D^107^@G+□                | TAZ G 107 * 006 C □ # @ 0 ^ ++ | TAZ G 107 * 006 C □ L @ 9 ^ ++ | G  | 100                                 | 6                                  | 1.1     | 6             | 60            | 72             | 10           | 12               | 12                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR19D^157^@G+□                | TAZ G 157 * 006 C □ # @ 0 ^ ++ | TAZ G 157 * 006 C □ L @ 9 ^ ++ | G  | 150                                 | 6                                  | 1.1     | 10            | 100           | 120            | 10           | 12               | 12                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR19D^227^@H+□                | TAZ H 227 * 006 C □ # @ 0 ^ ++ | TAZ H 227 * 006 C □ L @ 9 ^ ++ | H  | 220                                 | 6                                  | 0.9     | 10            | 100           | 120            | 10           | 12               | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19D^337^@H+□                | TAZ H 337 * 006 C □ # @ 0 ^ ++ | TAZ H 337 * 006 C □ L @ 9 ^ ++ | H  | 330                                 | 6                                  | 0.9     | 20            | 200           | 240            | 10           | 12               | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19F^225^@A+□                | TAZ A 225 * 010 C □ # @ 0 ^ ++ | TAZ A 225 * 010 C □ L @ 9 ^ ++ | A  | 2.2                                 | 10                                 | 12      | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR19F^335^@A+□                | TAZ A 335 * 010 C □ # @ 0 ^ ++ | TAZ A 335 * 010 C □ L @ 9 ^ ++ | A  | 3.3                                 | 10                                 | 12      | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR19F^475^@B+□                | TAZ B 475 * 010 C □ # @ 0 ^ ++ | TAZ B 475 * 010 C □ L @ 9 ^ ++ | B  | 4.7                                 | 10                                 | 8       | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19F^685^@B+□                | TAZ B 685 * 010 C □ # @ 0 ^ ++ | TAZ B 685 * 010 C □ L @ 9 ^ ++ | B  | 6.8                                 | 10                                 | 8       | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19F^106^@B+□                | TAZ B 106 * 010 C □ # @ 0 ^ ++ | TAZ B 106 * 010 C □ L @ 9 ^ ++ | B  | 10                                  | 10                                 | 8       | 1             | 10            | 12             | 8            | 10               | 10                                | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.75                            | 0.67                             | 0.30 |
| CWR19F^475^@C+□                | TAZ C 475 * 010 C □ # @ 0 ^ ++ | TAZ C 475 * 010 C □ L @ 9 ^ ++ | C  | 4.7                                 | 10                                 | 5.5     | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR19F^685^@C+□                | TAZ C 685 * 010 C □ # @ 0 ^ ++ | TAZ C 685 * 010 C □ L @ 9 ^ ++ | C  | 6.8                                 | 10                                 | 5.5     | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR19F^106^@C+□                | TAZ C 106 * 010 C □ # @ 0 ^ ++ | TAZ C 106 * 010 C □ L @ 9 ^ ++ | C  | 10                                  | 10                                 | 5.5     | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR19F^685^@D+□                | TAZ D 685 * 010 C □ # @ 0 ^ ++ | TAZ D 685 * 010 C □ L @ 9 ^ ++ | D  | 6.8                                 | 10                                 | 5       | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.080                           | 0.13                            | 0.11                             | 0.05                            | 0.63                            | 0.57                             | 0.25 |
| CWR19F^106^@D+□                | TAZ D 106 * 010 C □ # @ 0 ^ ++ | TAZ D 106 * 010 C □ L @ 9 ^ ++ | D  | 10                                  | 10                                 | 4       | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.080                           | 0.14                            | 0.13                             | 0.06                            | 0.57                            | 0.51                             | 0.23 |
| CWR19F^156^@D+□                | TAZ D 156 * 010 C □ # @ 0 ^ ++ | TAZ D 156 * 010 C □ L @ 9 ^ ++ | D  | 15                                  | 10                                 | 5       | 2             | 20            | 24             | 6            | 8                | 8                                 | 0.080                           | 0.13                            | 0.11                             | 0.05                            | 0.63                            | 0.57                             | 0.25 |
| CWR19F^106^@E+□                | TAZ E 106 * 010 C □ # @ 0 ^ ++ | TAZ E 106 * 010 C □ L @ 9 ^ ++ | E  | 10                                  | 10                                 | 3.5     | 1             | 10            | 12             | 6            | 8                | 8                                 | 0.090                           | 0.16                            | 0.14                             | 0.06                            | 0.56                            | 0.51                             | 0.22 |
| CWR19F^156^@E+□                | TAZ E 156 * 010 C □ # @ 0 ^ ++ | TAZ E 156 * 010 C □ L @ 9 ^ ++ | E  | 15                                  | 10                                 | 3       | 2             | 20            | 24             | 8            | 10               | 10                                | 0.090                           | 0.17                            | 0.16                             | 0.07                            | 0.52                            | 0.47                             | 0.21 |
| CWR19F^226^@E+□                | TAZ E 226 * 010 C □ # @ 0 ^ ++ | TAZ E 226 * 010 C □ L @ 9 ^ ++ | E  | 22                                  | 10                                 | 2       | 3             | 30            | 36             | 8            | 10               | 10                                | 0.090                           | 0.21                            | 0.19                             | 0.08                            | 0.42                            | 0.38                             | 0.17 |
| CWR19F^336^@F+□                | TAZ F 336 * 010 C □ # @ 0 ^ ++ | TAZ F 336 * 010 C □ L @ 9 ^ ++ | F  | 33                                  | 10                                 | 1.5     | 3             | 30            | 36             | 8            | 10               | 10                                | 0.100                           | 0.26                            | 0.23                             | 0.10                            | 0.39                            | 0.35                             | 0.15 |
| CWR19F^476^@F+□                | TAZ F 476 * 010 C □ # @ 0 ^ ++ | TAZ F 476 * 010 C □ L @ 9 ^ ++ | F  | 47                                  | 10                                 | 1.5     | 4             | 40            | 48             | 10           | 12               | 12                                | 0.100                           | 0.26                            | 0.23                             | 0.10                            | 0.39                            | 0.35                             | 0.15 |
| CWR19F^476^@G+□                | TAZ G 476 * 010 C □ # @ 0 ^ ++ | TAZ G 476 * 010 C □ L @ 9 ^ ++ | G  | 47                                  | 10                                 | 1       | 4             | 40            | 48             | 10           | 12               | 12                                | 0.125                           | 0.35                            | 0.32                             | 0.14                            | 0.35                            | 0.32                             | 0.14 |
| CWR19F^686^@G+□                | TAZ G 686 * 010 C □ # @ 0 ^ ++ | TAZ G 686 * 010 C □ L @ 9 ^ ++ | G  | 68                                  | 10                                 | 1.1     | 6             | 60            | 72             | 10           | 12               | 12                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR19F^107^@G+□                | TAZ G 107 * 010 C □ # @ 0 ^ ++ | TAZ G 107 * 010 C □ L @ 9 ^ ++ | G  | 100                                 | 10                                 | 1.1     | 10            | 100           | 120            | 10           | 12               | 12                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR19F^107^@H+□                | TAZ H 107 * 010 C □ # @ 0 ^ ++ | TAZ H 107 * 010 C □ L @ 9 ^ ++ | H  | 100                                 | 10                                 | 0.9     | 10            | 100           | 120            | 10           | 12               | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19F^157^@H+□                | TAZ H 157 * 010 C □ # @ 0 ^ ++ | TAZ H 157 * 010 C □ L @ 9 ^ ++ | H  | 150                                 | 10                                 | 0.9     | 15            | 150           | 180            | 10           | 12               | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19F^227^@H+□                | TAZ H 227 * 010 C □ # @ 0 ^ ++ | TAZ H 227 * 010 C □ L @ 9 ^ ++ | H  | 220                                 | 10                                 | 0.9     | 20            | 200           | 240            | 10           | 12               | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19F^157^@X+□                | TAZ X 157 * 010 C □ # @ 0 ^ ++ | TAZ X 157 * 010 C □ L @ 9 ^ ++ | X  | 150                                 | 10                                 | 0.9     | 15            | 150           | 180            | 10           | 12               | 12                                | 0.200                           | 0.47                            | 0.42                             | 0.19                            | 0.42                            | 0.38                             | 0.17 |

All technical data relates to ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.





# TAZ Series



## CWR19 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                | Parametric Specifications by Rating per MIL-PRF-55365/11 |                                     |                                    |         |       |           |        |    |    | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|--------------------------------|--------------------------------|--|-------------------------------------|------------------------------------|---------|-------|-----------|--------|----|----|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                                |                                | Cap<br>@ 120Hz<br>µF<br>@ 25°C                           | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |       |           | DF Max |    |    | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
| CWR19 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case   | +25°C                               | +85°C                              | +125°C  | +25°C | +85/125°C | -55°C  |    |    |                                   |                                 |                                 |                                  |                                 |                                 |                                  |      |
| CWR19H^105^@A+□                | TAZ A 105 * 015 C □ # @ 0 ^ ++ | TAZ A 105 * 015 C □ L @ 9 ^ ++ | A  | 1                                   | 15                                 | 15      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.87                            | 0.78                             | 0.35 |
| CWR19H^155^@A+□                | TAZ A 155 * 015 C □ # @ 0 ^ ++ | TAZ A 155 * 015 C □ L @ 9 ^ ++ | A  | 1.5                                 | 15                                 | 15      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.87                            | 0.78                             | 0.35 |
| CWR19H^225^@A+□                | TAZ A 225 * 015 C □ # @ 0 ^ ++ | TAZ A 225 * 015 C □ L @ 9 ^ ++ | A  | 2.2                                 | 15                                 | 15      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.87                            | 0.78                             | 0.35 |
| CWR19H^335^@B+□                | TAZ B 335 * 015 C □ # @ 0 ^ ++ | TAZ B 335 * 015 C □ L @ 9 ^ ++ | B  | 3.3                                 | 15                                 | 9       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.79                            | 0.71                             | 0.32 |
| CWR19H^475^@B+□                | TAZ B 475 * 015 C □ # @ 0 ^ ++ | TAZ B 475 * 015 C □ L @ 9 ^ ++ | B  | 4.7                                 | 15                                 | 5       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.12                            | 0.11                             | 0.05                            | 0.59                            | 0.53                             | 0.24 |
| CWR19H^475^@C+□                | TAZ C 475 * 015 C □ # @ 0 ^ ++ | TAZ C 475 * 015 C □ L @ 9 ^ ++ | C  | 4.7                                 | 15                                 | 5.5     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.075                           | 0.12                            | 0.11                             | 0.05                            | 0.64                            | 0.58                             | 0.26 |
| CWR19H^475^@D+□                | TAZ D 475 * 015 C □ # @ 0 ^ ++ | TAZ D 475 * 015 C □ L @ 9 ^ ++ | D  | 4.7                                 | 15                                 | 6       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.12                            | 0.10                             | 0.05                            | 0.69                            | 0.62                             | 0.28 |
| CWR19H^685^@D+□                | TAZ D 685 * 015 C □ # @ 0 ^ ++ | TAZ D 685 * 015 C □ L @ 9 ^ ++ | D  | 6.8                                 | 15                                 | 6       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.12                            | 0.10                             | 0.05                            | 0.69                            | 0.62                             | 0.28 |
| CWR19H^106^@D+□                | TAZ D 106 * 015 C □ # @ 0 ^ ++ | TAZ D 106 * 015 C □ L @ 9 ^ ++ | D  | 10                                  | 15                                 | 6       | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.080                           | 0.12                            | 0.10                             | 0.05                            | 0.69                            | 0.62                             | 0.28 |
| CWR19H^685^@E+□                | TAZ E 685 * 015 C □ # @ 0 ^ ++ | TAZ E 685 * 015 C □ L @ 9 ^ ++ | E  | 6.8                                 | 15                                 | 3       | 1     | 10        | 12     | 8  | 10 | 12                                | 0.090                           | 0.17                            | 0.16                             | 0.07                            | 0.52                            | 0.47                             | 0.21 |
| CWR19H^106^@E+□                | TAZ E 106 * 015 C □ # @ 0 ^ ++ | TAZ E 106 * 015 C □ L @ 9 ^ ++ | E  | 10                                  | 15                                 | 4       | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.090                           | 0.15                            | 0.14                             | 0.06                            | 0.60                            | 0.54                             | 0.24 |
| CWR19H^156^@E+□                | TAZ E 156 * 015 C □ # @ 0 ^ ++ | TAZ E 156 * 015 C □ L @ 9 ^ ++ | E  | 15                                  | 15                                 | 4       | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.090                           | 0.15                            | 0.14                             | 0.06                            | 0.60                            | 0.54                             | 0.24 |
| CWR19H^156^@F+□                | TAZ F 156 * 015 C □ # @ 0 ^ ++ | TAZ F 156 * 015 C □ L @ 9 ^ ++ | F  | 15                                  | 15                                 | 3       | 2     | 20        | 24     | 8  | 10 | 10                                | 0.100                           | 0.18                            | 0.16                             | 0.07                            | 0.55                            | 0.49                             | 0.22 |
| CWR19H^226^@F+□                | TAZ F 226 * 015 C □ # @ 0 ^ ++ | TAZ F 226 * 015 C □ L @ 9 ^ ++ | F  | 22                                  | 15                                 | 3       | 3     | 30        | 36     | 8  | 10 | 10                                | 0.100                           | 0.18                            | 0.16                             | 0.07                            | 0.55                            | 0.49                             | 0.22 |
| CWR19H^336^@F+□                | TAZ F 336 * 015 C □ # @ 0 ^ ++ | TAZ F 336 * 015 C □ L @ 9 ^ ++ | F  | 33                                  | 15                                 | 3       | 5     | 50        | 60     | 6  | 8  | 8                                 | 0.100                           | 0.18                            | 0.16                             | 0.07                            | 0.55                            | 0.49                             | 0.22 |
| CWR19H^336^@G+□                | TAZ G 336 * 015 C □ # @ 0 ^ ++ | TAZ G 336 * 015 C □ L @ 9 ^ ++ | G  | 33                                  | 15                                 | 1.1     | 6     | 60        | 72     | 8  | 10 | 10                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR19H^476^@G+□                | TAZ G 476 * 015 C □ # @ 0 ^ ++ | TAZ G 476 * 015 C □ L @ 9 ^ ++ | G  | 47                                  | 15                                 | 1.1     | 10    | 100       | 120    | 8  | 10 | 10                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR19H^686^@G+□                | TAZ G 686 * 015 C □ # @ 0 ^ ++ | TAZ G 686 * 015 C □ L @ 9 ^ ++ | G  | 68                                  | 15                                 | 1.1     | 10    | 100       | 120    | 8  | 10 | 10                                | 0.125                           | 0.34                            | 0.30                             | 0.13                            | 0.37                            | 0.33                             | 0.15 |
| CWR19H^476^@H+□                | TAZ H 476 * 015 C □ # @ 0 ^ ++ | TAZ H 476 * 015 C □ L @ 9 ^ ++ | H  | 47                                  | 15                                 | 0.9     | 10    | 100       | 120    | 8  | 10 | 10                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19H^686^@H+□                | TAZ H 686 * 015 C □ # @ 0 ^ ++ | TAZ H 686 * 015 C □ L @ 9 ^ ++ | H  | 68                                  | 15                                 | 0.9     | 10    | 100       | 120    | 8  | 10 | 10                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19H^107^@H+□                | TAZ H 107 * 015 C □ # @ 0 ^ ++ | TAZ H 107 * 015 C □ L @ 9 ^ ++ | H  | 100                                 | 15                                 | 0.9     | 15    | 150       | 180    | 10 | 12 | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19J^684^@A+□                | TAZ A 684 * 020 C □ # @ 0 ^ ++ | TAZ A 684 * 020 C □ L @ 9 ^ ++ | A  | 0.68                                | 20                                 | 15      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.87                            | 0.78                             | 0.35 |
| CWR19J^105^@A+□                | TAZ A 105 * 020 C □ # @ 0 ^ ++ | TAZ A 105 * 020 C □ L @ 9 ^ ++ | A  | 1                                   | 20                                 | 15      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.87                            | 0.78                             | 0.35 |
| CWR19J^155^@B+□                | TAZ B 155 * 020 C □ # @ 0 ^ ++ | TAZ B 155 * 020 C □ L @ 9 ^ ++ | B  | 1.5                                 | 20                                 | 9       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.79                            | 0.71                             | 0.32 |
| CWR19J^225^@B+□                | TAZ B 225 * 020 C □ # @ 0 ^ ++ | TAZ B 225 * 020 C □ L @ 9 ^ ++ | B  | 2.2                                 | 20                                 | 9       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.09                            | 0.08                             | 0.04                            | 0.79                            | 0.71                             | 0.32 |
| CWR19J^335^@D+□                | TAZ D 335 * 020 C □ # @ 0 ^ ++ | TAZ D 335 * 020 C □ L @ 9 ^ ++ | D  | 3.3                                 | 20                                 | 6       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.12                            | 0.10                             | 0.05                            | 0.69                            | 0.62                             | 0.28 |
| CWR19J^475^@E+□                | TAZ E 475 * 020 C □ # @ 0 ^ ++ | TAZ E 475 * 020 C □ L @ 9 ^ ++ | E  | 4.7                                 | 20                                 | 6       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.090                           | 0.12                            | 0.11                             | 0.05                            | 0.73                            | 0.66                             | 0.29 |
| CWR19J^685^@E+□                | TAZ E 685 * 020 C □ # @ 0 ^ ++ | TAZ E 685 * 020 C □ L @ 9 ^ ++ | E  | 6.8                                 | 20                                 | 5       | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.090                           | 0.13                            | 0.12                             | 0.05                            | 0.67                            | 0.60                             | 0.27 |
| CWR19J^106^@E+□                | TAZ E 106 * 020 C □ # @ 0 ^ ++ | TAZ E 106 * 020 C □ L @ 9 ^ ++ | E  | 10                                  | 20                                 | 5       | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.090                           | 0.13                            | 0.12                             | 0.05                            | 0.67                            | 0.60                             | 0.27 |
| CWR19J^106^@F+□                | TAZ F 106 * 020 C □ # @ 0 ^ ++ | TAZ F 106 * 020 C □ L @ 9 ^ ++ | F  | 10                                  | 20                                 | 3       | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.100                           | 0.18                            | 0.16                             | 0.07                            | 0.55                            | 0.49                             | 0.22 |
| CWR19J^156^@F+□                | TAZ F 156 * 020 C □ # @ 0 ^ ++ | TAZ F 156 * 020 C □ L @ 9 ^ ++ | F  | 15                                  | 20                                 | 3       | 3     | 30        | 36     | 6  | 8  | 8                                 | 0.100                           | 0.18                            | 0.16                             | 0.07                            | 0.55                            | 0.49                             | 0.22 |
| CWR19J^226^@G+□                | TAZ G 226 * 020 C □ # @ 0 ^ ++ | TAZ G 226 * 020 C □ L @ 9 ^ ++ | G  | 22                                  | 20                                 | 2.5     | 4     | 40        | 48     | 6  | 8  | 8                                 | 0.125                           | 0.22                            | 0.20                             | 0.09                            | 0.56                            | 0.50                             | 0.22 |
| CWR19J^336^@H+□                | TAZ H 336 * 020 C □ # @ 0 ^ ++ | TAZ H 336 * 020 C □ L @ 9 ^ ++ | H  | 33                                  | 20                                 | 0.9     | 6     | 60        | 72     | 8  | 10 | 10                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19J^476^@H+□                | TAZ H 476 * 020 C □ # @ 0 ^ ++ | TAZ H 476 * 020 C □ L @ 9 ^ ++ | H  | 47                                  | 20                                 | 0.9     | 10    | 100       | 120    | 8  | 10 | 10                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19J^476^@X+□                | TAZ X 476 * 020 C □ # @ 0 ^ ++ | TAZ X 476 * 020 C □ L @ 9 ^ ++ | X  | 47                                  | 20                                 | 0.9     | 10    | 100       | 120    | 8  | 10 | 10                                | 0.200                           | 0.47                            | 0.42                             | 0.19                            | 0.42                            | 0.38                             | 0.17 |
| CWR19K^474^@A+□                | TAZ A 474 * 025 C □ # @ 0 ^ ++ | TAZ A 474 * 025 C □ L @ 9 ^ ++ | A  | 0.47                                | 25                                 | 15      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.05                             | 0.02                            | 0.87                            | 0.78                             | 0.35 |
| CWR19K^105^@B+□                | TAZ B 105 * 025 C □ # @ 0 ^ ++ | TAZ B 105 * 025 C □ L @ 9 ^ ++ | B  | 1                                   | 25                                 | 10      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.08                            | 0.08                             | 0.03                            | 0.84                            | 0.75                             | 0.33 |
| CWR19K^225^@D+□                | TAZ D 225 * 025 C □ # @ 0 ^ ++ | TAZ D 225 * 025 C □ L @ 9 ^ ++ | D  | 2.2                                 | 25                                 | 6       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.12                            | 0.10                             | 0.05                            | 0.69                            | 0.62                             | 0.28 |
| CWR19K^335^@E+□                | TAZ E 335 * 025 C □ # @ 0 ^ ++ | TAZ E 335 * 025 C □ L @ 9 ^ ++ | E  | 3.3                                 | 25                                 | 4       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.090                           | 0.15                            | 0.14                             | 0.06                            | 0.60                            | 0.54                             | 0.24 |
| CWR19K^685^@F+□                | TAZ F 685 * 025 C □ # @ 0 ^ ++ | TAZ F 685 * 025 C □ L @ 9 ^ ++ | F  | 6.8                                 | 25                                 | 3       | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.100                           | 0.18                            | 0.16                             | 0.07                            | 0.55                            | 0.49                             | 0.22 |
| CWR19K^156^@G+□                | TAZ G 156 * 025 C □ # @ 0 ^ ++ | TAZ G 156 * 025 C □ L @ 9 ^ ++ | G  | 15                                  | 25                                 | 1.4     | 4     | 40        | 48     | 6  | 8  | 8                                 | 0.125                           | 0.30                            | 0.27                             | 0.12                            | 0.42                            | 0.38                             | 0.17 |
| CWR19K^226^@G+□                | TAZ G 226 * 025 C □ # @ 0 ^ ++ | TAZ G 226 * 025 C □ L @ 9 ^ ++ | G  | 22                                  | 25                                 | 1.4     | 6     | 60        | 72     | 6  | 8  | 8                                 | 0.125                           | 0.30                            | 0.27                             | 0.12                            | 0.42                            | 0.38                             | 0.17 |
| CWR19K^226^@H+□                | TAZ H 226 * 025 C □ # @ 0 ^ ++ | TAZ H 226 * 025 C □ L @ 9 ^ ++ | H  | 22                                  | 25                                 | 0.9     | 6     | 60        | 72     | 6  | 8  | 8                                 | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19K^336^@H+□                | TAZ H 336 * 025 C □ # @ 0 ^ ++ | TAZ H 336 * 025 C □ L @ 9 ^ ++ | H  | 33                                  | 25                                 | 0.9     | 10    | 100       | 120    | 8  | 10 | 10                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19M^334^@A+□                | TAZ A 334 * 035 C □ # @ 0 ^ ++ | TAZ A 334 * 035 C □ L @ 9 ^ ++ | A  | 0.33                                | 35                                 | 22      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.05                            | 0.04                             | 0.02                            | 1.05                            | 0.94                             | 0.42 |
| CWR19M^685^@G+□                | TAZ G 685 * 035 C □ # @ 0 ^ ++ | TAZ G 685 * 035 C □ L @ 9 ^ ++ | G  | 6.8                                 | 35                                 | 1.5     | 3     | 30        | 36     | 6  | 8  | 8                                 | 0.125                           | 0.29                            | 0.26                             | 0.12                            | 0.43                            | 0.39                             | 0.17 |
| CWR19M^106^@H+□                | TAZ H 106 * 035 C □ # @ 0 ^ ++ | TAZ H 106 * 035 C □ L @ 9 ^ ++ | H  | 10                                  | 35                                 | 0.9     | 4     | 40        | 48     | 8  | 10 | 10                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR19M^156^@X+□                | TAZ X 156 * 035 C □ # @ 0 ^ ++ | TAZ X 156 * 035 C □ L @ 9 ^ ++ | X  | 15                                  | 35                                 | 0.9     | 6     | 60        | 72     | 6  | 8  | 8                                 | 0.200                           | 0.47                            | 0.42                             | 0.19                            | 0.42                            | 0.38                             | 0.17 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# TAZ Series



## CWR29 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level



A low ESR version of CWR09 and CWR19 that is fully qualified to MIL-PRF-55365/11, the CWR29 series represents the most flexible of surface mount form factors and the optimum power handling for all filtering applications. It is offered in nine case sizes (the original A through H of CWR09 and adding the new X case size).

The molded body / compliant termination construction ensures no TCE mismatch with any substrate. This construction is compatible with a wide range of SMT board assembly processes including wave or reflow solder, conductive epoxy or compression bonding techniques. The parts also carry full polarity and capacitance / voltage marking.


The five smaller cases are characterized by their low profile construction, with the A case being the world's smallest molded military tantalum chip.

The series is qualified to MIL-PRF-55365 Weibull "B", "C", "D" and "T" levels, with all surge options ("A", "B" & "C") available.

For Space Level applications, AVX SRC 9000 qualification is recommended (see ratings table for part number availability).

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these are "H", "K", "C" and "B" termination, respectively, per MIL-PRF-55365). In addition, the molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.



### MARKING

(White marking on black body)



**Polarity Stripe (+)**

**Capacitance Code  
Rated Voltage**

### CASE DIMENSIONS:

millimeters (inches)

| Case Code | Length (L)<br>±0.38 (0.015) | Width (W)<br>±0.38 (0.015) | Height (H)<br>±0.38 (0.015) | Term. Width (W <sub>t</sub> )           | Term. Length (A)<br>+0.25/-0.13<br>(+0.010/-0.005) | S min        | Typical Weight (g) |
|-----------|-----------------------------|----------------------------|-----------------------------|---|--|--------------|--------------------|
| A         | 2.54 (0.100)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 0.38 (0.015) | 0.016              |
| B         | 3.81 (0.150)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 1.65 (0.065) | 0.025              |
| C         | 5.08 (0.200)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 2.92 (0.115) | 0.035              |
| D         | 3.81 (0.150)                | 2.54 (0.100)               | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 1.65 (0.065) | 0.045              |
| E         | 5.08 (0.200)                | 2.54 (0.100)               | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 2.92 (0.115) | 0.065              |
| F         | 5.59 (0.220)                | 3.43 (0.135)               | 1.78 (0.070)                | 3.30±0.13<br>(0.130±0.005)              | 0.76 (0.030)                                       | 3.43 (0.135) | 0.125              |
| G         | 6.73 (0.265)                | 2.79 (0.110)               | 2.79 (0.110)                | 2.67±0.13<br>(0.105±0.005)              | 1.27 (0.050)                                       | 3.56 (0.140) | 0.205              |
| H         | 7.24 (0.285)                | 3.81 (0.150)               | 2.79 (0.110)                | 3.68±0.13/-0.51<br>(0.145+0.005/-0.020) | 1.27 (0.050)                                       | 4.06 (0.160) | 0.335              |
| X         | 6.93 (0.273)                | 5.41 (0.213)               | 2.74 (0.108)                | 3.05±0.13<br>(0.120±0.005)              | 1.19 (0.047)                                       | N/A          | 0.420              |

### CWR29-MIL-PRF 55365/11

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated voltage DC (V <sub>R</sub> ) at 85°C |        |         |         |         |         |         |         |
|-------------|------|--|--------|---------|---------|---------|---------|---------|---------|
| µF          | Code | 4V (C)                                     | 6V (D) | 10V (F) | 15V (H) | 20V (J) | 25V (K) | 35V (M) | 50V (N) |
| 0.10        | 104  |  |        |         |         |         |         |         | A       |
| 0.15        | 154  |  |        |         |         |         |         |         | A       |
| 0.22        | 224  |  |        |         |         |         |         | A       | B       |
| 0.33        | 334  |  |        |         |         |         | A       | A       | B       |
| 0.47        | 474  |  |        |         |         | A       | A       | B       | C       |
| 0.68        | 684  |  |        |         | A       | A/B     | B       | C       | D       |
| 1.0         | 105  |  |        | A       | A       | A/B     | B/C     | D       | E       |
| 1.5         | 155  |  | A      |         | A/B     | B/C     | D       | E       | F       |
| 2.2         | 225  | A  |        | A/B     | A/C     | B/D     | D/E     |         | F       |
| 3.3         | 335  | A  | A/B    | A/C     | B/D     | D/E     | E       | F       | G       |
| 4.7         | 475  | A/B  | A/C    | B/C/D   | B/C/D/E | D/E     | E       | F       | G       |
| 6.8         | 685  | A/C  | B/D    | B/C/D/E | D/E     | E/F     | F/G     | G/H     | H       |
| 10          | 106  | B/D  | B/E    | B/C/D/E | D/E/F   | E/F     | G       | H       |         |
| 15          | 156  | B/E  | B/D/E  | D/E/F   | E/F     | F/G     | G/H     | X       |         |
| 22          | 226  | B/D  | D/E/F  | E       | F/G     | G/H     | G/H     |         |         |
| 33          | 336  | D/E/F                                      | E      | F/G     | F/G/H   | H       | H       |         |         |
| 47          | 476  | E  | F/G    | F/G/H   | G/H     | H/X     |         |         |         |
| 68          | 686  | E/G  | F/G/H  | G       | G/H     |         |         |         |         |
| 100         | 107  | F/H  | G      | G/H     | H       |         |         |         |         |
| 150         | 157  | G  | G      | H/X     |         |         |         |         |         |
| 220         | 227  | H  | H      | H       |         |         |         |         |         |
| 330         | 337  | H  | H      |         |         |         |         |         |         |



# TAZ Series



## CWR29 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level

### HOW TO ORDER

#### COTS-PLUS & MIL QPL (CWR29):

|             |                  |  |   |   |  |   |   |   |   |  |   |
|-------------|------------------|--|---|---|--|---|---|---|---|--|---|
| <b>TAZ</b>  | <b>H</b>         | <b>227</b>   | <b>*</b>  | <b>006</b>  | <b>C</b>   | <b>□</b>  | <b>#</b>  | <b>@</b>  | <b>0</b>  | <b>^</b>   | <b>++</b>   |
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>S = Std. Conformance<br>L = Group A<br><br>M = MIL (JAN) CWR29 | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>Z = Non-ER | <b>Qualification Level</b><br>0 = N/A<br>T = T Level<br>9 = SRC9000 | <b>Termination Finish</b><br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated<br>7 = Matte Sn (COTS-Plus only) | <b>Surge Test Option</b><br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

#### CWR29 P/N CROSS REFERENCE:

|              |   |  |  |   |  |                  |  |  |
|--------------|---|--|--|---|--|------------------|--|--|
| <b>CWR29</b> | <b>D</b>  | <b>^</b>   | <b>227</b>   | <b>*</b>  | <b>@</b>   | <b>H</b>         | <b>+</b>   | <b>□</b>   |
| <b>Type</b>  | <b>Voltage Code</b><br>C = 4Vdc<br>D = 6Vdc<br>F = 10Vdc<br>H = 15Vdc<br>J = 20Vdc<br>K = 25Vdc<br>M = 35Vdc<br>N = 50Vdc | <b>Termination Finish</b><br>H = Solder Plated<br>K = Solder Fused<br>C = Hot Solder Dipped<br>B = Gold Plated | <b>Capacitance Code</b><br>pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>T = T Level<br>A = Non-ER | <b>Case Size</b> | <b>Surge Test Option</b><br>A = 10 cycles, +25°C<br>B = 10 cycles, -55°C & +85°C<br>C = 10 cycles, -55°C & +85°C before Weibull<br>Z = None required | <b>Packaging</b><br>Bulk = Standard<br>TR = 7" T&R<br>TR13 = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. |

For RoHS compliant products, please select correct termination style.

#### SPACE LEVEL OPTIONS TO SRC9000\*:

|             |                  |  |   |   |  |   |  |   |   |   |  |
|-------------|------------------|--|---|---|--|---|--|---|---|---|--|
| <b>TAZ</b>  | <b>H</b>         | <b>227</b>   | <b>*</b>  | <b>006</b>  | <b>C</b>   | <b>□</b>  | <b>L</b>                               | <b>@</b>  | <b>9</b>                                  | <b>^</b>  | <b>++</b>  |
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>L = Group A | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf. | <b>Qualification Level</b><br>9 = SRC9000 | <b>Termination Finish</b><br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated | <b>Surge Test Option</b><br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |     |      |      |      |      |      |      |  |
|------------------------------------|---|-----|-----|------|------|------|------|------|------|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |     |      |      |      |      |      |      |  |
| Capacitance Range:                 | 0.10 µF to 330 µF   |     |     |      |      |      |      |      |      |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |     |      |      |      |      |      |      |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6   | 10   | 15   | 20   | 25   | 35   | 50   |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4   | 6.7  | 10   | 13.3 | 16.7 | 23.3 | 33.3 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 5.3 | 8   | 13.3 | 20   | 26.7 | 33.3 | 46.7 | 66.7 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 3.5 | 5.3 | 8.7  | 13.3 | 17.8 | 22.2 | 31.1 | 44.5 |  |
| Temperature Range:                 | -55°C to +125°C   |     |     |      |      |      |      |      |      |  |



# TAZ Series



## CWR29 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                | Parametric Specifications by Rating per MIL-PRF-55365/11 |                                     |                                    |         |       |       |        |       |       | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|--------------------------------|--------------------------------|--|-------------------------------------|------------------------------------|---------|-------|-------|--------|-------|-------|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                                |                                | Cap<br>@ 120Hz<br>µF<br>@ 25°C                           | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |       |       | DF Max |       |       | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
| CWR29 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case   | +25°C                               | +85°C                              | +125°C  | +25°C | +85°C | +125°C | +25°C | +85°C | +125°C                            | W                               | A                               | A                                | A                               | V                               | V                                | V    |
| CWR29C^225^@A+□                | TAZ A 225 * 004 L □ # @ 0 ^ ++ | TAZ A 225 * 004 L □ L @ 9 ^ ++ | A  | 2.2                                 | 4                                  | 4       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.11                            | 0.10                             | 0.04                            | 0.45                            | 0.40                             | 0.18 |
| CWR29C^335^@A+□                | TAZ A 335 * 004 L □ # @ 0 ^ ++ | TAZ A 335 * 004 L □ L @ 9 ^ ++ | A  | 3.3                                 | 4                                  | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29C^475^@A+□                | TAZ A 475 * 004 L □ # @ 0 ^ ++ | TAZ A 475 * 004 L □ L @ 9 ^ ++ | A  | 4.7                                 | 4                                  | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29C^475^@B+□                | TAZ B 475 * 004 L □ # @ 0 ^ ++ | TAZ B 475 * 004 L □ L @ 9 ^ ++ | B  | 4.7                                 | 4                                  | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29C^685^@A+□                | TAZ A 685 * 004 L □ # @ 0 ^ ++ | TAZ A 685 * 004 L □ L @ 9 ^ ++ | A  | 6.8                                 | 4                                  | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29C^685^@C+□                | TAZ C 685 * 004 L □ # @ 0 ^ ++ | TAZ C 685 * 004 L □ L @ 9 ^ ++ | C  | 6.8                                 | 4                                  | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |
| CWR29C^106^@B+□                | TAZ B 106 * 004 L □ # @ 0 ^ ++ | TAZ B 106 * 004 L □ L @ 9 ^ ++ | B  | 10                                  | 4                                  | 3.2     | 1     | 10    | 12     | 8     | 10    | 10                                | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29C^106^@D+□                | TAZ D 106 * 004 L □ # @ 0 ^ ++ | TAZ D 106 * 004 L □ L @ 9 ^ ++ | D  | 10                                  | 4                                  | 1.3     | 1     | 10    | 12     | 8     | 10    | 10                                | 0.080                           | 0.25                            | 0.22                             | 0.10                            | 0.32                            | 0.29                             | 0.13 |
| CWR29C^156^@B+□                | TAZ B 156 * 004 L □ # @ 0 ^ ++ | TAZ B 156 * 004 L □ L @ 9 ^ ++ | B  | 15                                  | 4                                  | 3.2     | 1     | 10    | 12     | 8     | 10    | 10                                | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29C^156^@E+□                | TAZ E 156 * 004 L □ # @ 0 ^ ++ | TAZ E 156 * 004 L □ L @ 9 ^ ++ | E  | 15                                  | 4                                  | 1       | 1     | 10    | 12     | 8     | 10    | 12                                | 0.090                           | 0.30                            | 0.27                             | 0.12                            | 0.30                            | 0.27                             | 0.12 |
| CWR29C^226^@B+□                | TAZ B 226 * 004 L □ # @ 0 ^ ++ | TAZ B 226 * 004 L □ L @ 9 ^ ++ | B  | 22                                  | 4                                  | 3.2     | 1     | 10    | 12     | 8     | 10    | 10                                | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29C^226^@D+□                | TAZ D 226 * 004 L □ # @ 0 ^ ++ | TAZ D 226 * 004 L □ L @ 9 ^ ++ | D  | 22                                  | 4                                  | 1.3     | 1     | 10    | 12     | 8     | 10    | 12                                | 0.080                           | 0.25                            | 0.22                             | 0.10                            | 0.32                            | 0.29                             | 0.13 |
| CWR29C^336^@D+□                | TAZ D 336 * 004 L □ # @ 0 ^ ++ | TAZ D 336 * 004 L □ L @ 9 ^ ++ | D  | 33                                  | 4                                  | 1.3     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.080                           | 0.25                            | 0.22                             | 0.10                            | 0.32                            | 0.29                             | 0.13 |
| CWR29C^336^@E+□                | TAZ E 336 * 004 L □ # @ 0 ^ ++ | TAZ E 336 * 004 L □ L @ 9 ^ ++ | E  | 33                                  | 4                                  | 0.9     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.090                           | 0.32                            | 0.28                             | 0.13                            | 0.28                            | 0.26                             | 0.11 |
| CWR29C^336^@F+□                | TAZ F 336 * 004 L □ # @ 0 ^ ++ | TAZ F 336 * 004 L □ L @ 9 ^ ++ | F  | 33                                  | 4                                  | 0.6     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.100                           | 0.41                            | 0.37                             | 0.16                            | 0.24                            | 0.22                             | 0.10 |
| CWR29C^476^@E+□                | TAZ E 476 * 004 L □ # @ 0 ^ ++ | TAZ E 476 * 004 L □ L @ 9 ^ ++ | E  | 47                                  | 4                                  | 0.9     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.090                           | 0.32                            | 0.28                             | 0.13                            | 0.28                            | 0.26                             | 0.11 |
| CWR29C^686^@E+□                | TAZ E 686 * 004 L □ # @ 0 ^ ++ | TAZ E 686 * 004 L □ L @ 9 ^ ++ | E  | 68                                  | 4                                  | 0.9     | 3     | 30    | 36     | 8     | 10    | 12                                | 0.090                           | 0.32                            | 0.28                             | 0.13                            | 0.28                            | 0.26                             | 0.11 |
| CWR29C^686^@G+□                | TAZ G 686 * 004 L □ # @ 0 ^ ++ | TAZ G 686 * 004 L □ L @ 9 ^ ++ | G  | 68                                  | 4                                  | 0.275   | 3     | 30    | 36     | 10    | 12    | 12                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29C^107^@F+□                | TAZ F 107 * 004 L □ # @ 0 ^ ++ | TAZ F 107 * 004 L □ L @ 9 ^ ++ | F  | 100                                 | 4                                  | 0.55    | 4     | 40    | 48     | 10    | 12    | 12                                | 0.100                           | 0.43                            | 0.38                             | 0.17                            | 0.23                            | 0.21                             | 0.09 |
| CWR29C^107^@H+□                | TAZ H 107 * 004 L □ # @ 0 ^ ++ | TAZ H 107 * 004 L □ L @ 9 ^ ++ | H  | 100                                 | 4                                  | 0.18    | 4     | 40    | 48     | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29C^157^@G+□                | TAZ G 157 * 004 L □ # @ 0 ^ ++ | TAZ G 157 * 004 L □ L @ 9 ^ ++ | G  | 150                                 | 4                                  | 0.25    | 6     | 60    | 72     | 10    | 12    | 12                                | 0.125                           | 0.71                            | 0.64                             | 0.28                            | 0.18                            | 0.16                             | 0.07 |
| CWR29C^227^@H+□                | TAZ H 227 * 004 L □ # @ 0 ^ ++ | TAZ H 227 * 004 L □ L @ 9 ^ ++ | H  | 220                                 | 4                                  | 0.2     | 8     | 80    | 96     | 10    | 12    | 12                                | 0.150                           | 0.87                            | 0.78                             | 0.35                            | 0.17                            | 0.16                             | 0.07 |
| CWR29C^337^@H+□                | TAZ H 337 * 004 L □ # @ 0 ^ ++ | TAZ H 337 * 004 L □ L @ 9 ^ ++ | H  | 330                                 | 4                                  | 0.18    | 10    | 100   | 120    | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29D^155^@A+□                | TAZ A 155 * 006 L □ # @ 0 ^ ++ | TAZ A 155 * 006 L □ L @ 9 ^ ++ | A  | 1.5                                 | 6                                  | 4       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.11                            | 0.10                             | 0.04                            | 0.45                            | 0.40                             | 0.18 |
| CWR29D^335^@A+□                | TAZ A 335 * 006 L □ # @ 0 ^ ++ | TAZ A 335 * 006 L □ L @ 9 ^ ++ | A  | 3.3                                 | 6                                  | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29D^335^@B+□                | TAZ B 335 * 006 L □ # @ 0 ^ ++ | TAZ B 335 * 006 L □ L @ 9 ^ ++ | B  | 3.3                                 | 6                                  | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29D^475^@A+□                | TAZ A 475 * 006 L □ # @ 0 ^ ++ | TAZ A 475 * 006 L □ L @ 9 ^ ++ | A  | 4.7                                 | 6                                  | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29D^475^@C+□                | TAZ C 475 * 006 L □ # @ 0 ^ ++ | TAZ C 475 * 006 L □ L @ 9 ^ ++ | C  | 4.7                                 | 6                                  | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |
| CWR29D^685^@B+□                | TAZ B 685 * 006 L □ # @ 0 ^ ++ | TAZ B 685 * 006 L □ L @ 9 ^ ++ | B  | 6.8                                 | 6                                  | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29D^685^@D+□                | TAZ D 685 * 006 L □ # @ 0 ^ ++ | TAZ D 685 * 006 L □ L @ 9 ^ ++ | D  | 6.8                                 | 6                                  | 1.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.23                            | 0.21                             | 0.09                            | 0.35                            | 0.31                             | 0.14 |
| CWR29D^106^@B+□                | TAZ B 106 * 006 L □ # @ 0 ^ ++ | TAZ B 106 * 006 L □ L @ 9 ^ ++ | B  | 10                                  | 6                                  | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29D^106^@E+□                | TAZ E 106 * 006 L □ # @ 0 ^ ++ | TAZ E 106 * 006 L □ L @ 9 ^ ++ | E  | 10                                  | 6                                  | 1       | 1     | 10    | 12     | 8     | 10    | 12                                | 0.090                           | 0.30                            | 0.27                             | 0.12                            | 0.30                            | 0.27                             | 0.12 |
| CWR29D^156^@B+□                | TAZ B 156 * 006 L □ # @ 0 ^ ++ | TAZ B 156 * 006 L □ L @ 9 ^ ++ | B  | 15                                  | 6                                  | 3.2     | 1     | 10    | 12     | 8     | 10    | 10                                | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29D^156^@D+□                | TAZ D 156 * 006 L □ # @ 0 ^ ++ | TAZ D 156 * 006 L □ L @ 9 ^ ++ | D  | 15                                  | 6                                  | 1.7     | 1     | 10    | 12     | 8     | 10    | 12                                | 0.080                           | 0.22                            | 0.20                             | 0.09                            | 0.37                            | 0.33                             | 0.15 |
| CWR29D^156^@E+□                | TAZ E 156 * 006 L □ # @ 0 ^ ++ | TAZ E 156 * 006 L □ L @ 9 ^ ++ | E  | 15                                  | 6                                  | 0.9     | 1     | 10    | 12     | 8     | 10    | 12                                | 0.090                           | 0.32                            | 0.28                             | 0.13                            | 0.28                            | 0.26                             | 0.11 |
| CWR29D^226^@D+□                | TAZ D 226 * 006 L □ # @ 0 ^ ++ | TAZ D 226 * 006 L □ L @ 9 ^ ++ | D  | 22                                  | 6                                  | 1.7     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.22                            | 0.20                             | 0.09                            | 0.37                            | 0.33                             | 0.15 |
| CWR29D^226^@E+□                | TAZ E 226 * 006 L □ # @ 0 ^ ++ | TAZ E 226 * 006 L □ L @ 9 ^ ++ | E  | 22                                  | 6                                  | 1       | 2     | 20    | 24     | 8     | 10    | 12                                | 0.090                           | 0.30                            | 0.27                             | 0.12                            | 0.30                            | 0.27                             | 0.12 |
| CWR29D^226^@F+□                | TAZ F 226 * 006 L □ # @ 0 ^ ++ | TAZ F 226 * 006 L □ L @ 9 ^ ++ | F  | 22                                  | 6                                  | 0.6     | 2     | 20    | 24     | 8     | 10    | 12                                | 0.100                           | 0.41                            | 0.37                             | 0.16                            | 0.24                            | 0.22                             | 0.10 |
| CWR29D^336^@E+□                | TAZ E 336 * 006 L □ # @ 0 ^ ++ | TAZ E 336 * 006 L □ L @ 9 ^ ++ | E  | 33                                  | 6                                  | 1       | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.090                           | 0.30                            | 0.27                             | 0.12                            | 0.30                            | 0.27                             | 0.12 |
| CWR29D^476^@F+□                | TAZ F 476 * 006 L □ # @ 0 ^ ++ | TAZ F 476 * 006 L □ L @ 9 ^ ++ | F  | 47                                  | 6                                  | 1       | 3     | 30    | 36     | 8     | 10    | 12                                | 0.100                           | 0.32                            | 0.28                             | 0.13                            | 0.32                            | 0.28                             | 0.13 |
| CWR29D^476^@G+□                | TAZ G 476 * 006 L □ # @ 0 ^ ++ | TAZ G 476 * 006 L □ L @ 9 ^ ++ | G  | 47                                  | 6                                  | 0.275   | 3     | 30    | 36     | 10    | 12    | 12                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29D^686^@F+□                | TAZ F 686 * 006 L □ # @ 0 ^ ++ | TAZ F 686 * 006 L □ L @ 9 ^ ++ | F  | 68                                  | 6                                  | 0.4     | 4     | 40    | 48     | 10    | 12    | 12                                | 0.100                           | 0.50                            | 0.45                             | 0.20                            | 0.20                            | 0.18                             | 0.08 |
| CWR29D^686^@G+□                | TAZ G 686 * 006 L □ # @ 0 ^ ++ | TAZ G 686 * 006 L □ L @ 9 ^ ++ | G  | 68                                  | 6                                  | 0.25    | 4     | 40    | 48     | 10    | 12    | 12                                | 0.125                           | 0.71                            | 0.64                             | 0.28                            | 0.18                            | 0.16                             | 0.07 |
| CWR29D^686^@H+□                | TAZ H 686 * 006 L □ # @ 0 ^ ++ | TAZ H 686 * 006 L □ L @ 9 ^ ++ | H  | 68                                  | 6                                  | 0.18    | 4     | 40    | 48     | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29D^107^@G+□                | TAZ G 107 * 006 L □ # @ 0 ^ ++ | TAZ G 107 * 006 L □ L @ 9 ^ ++ | G  | 100                                 | 6                                  | 0.275   | 6     | 60    | 72     | 10    | 12    | 12                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29D^157^@G+□                | TAZ G 157 * 006 L □ # @ 0 ^ ++ | TAZ G 157 * 006 L □ L @ 9 ^ ++ | G  | 150                                 | 6                                  | 0.275   | 10    | 100   | 120    | 10    | 12    | 12                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29D^227^@H+□                | TAZ H 227 * 006 L □ # @ 0 ^ ++ | TAZ H 227 * 006 L □ L @ 9 ^ ++ | H  | 220                                 | 6                                  | 0.18    | 10    | 100   | 120    | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29D^337^@H+□                | TAZ H 337 * 006 L □ # @ 0 ^ ++ | TAZ H 337 * 006 L □ L @ 9 ^ ++ | H  | 330                                 | 6                                  | 0.18    | 20    | 200   | 240    | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29F^105^@A+□                | TAZ A 105 * 010 L □ # @ 0 ^ ++ | TAZ A 105 * 010 L □ L @ 9 ^ ++ | A  | 1                                   | 10                                 | 5       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.10                            | 0.09                             | 0.04                            | 0.50                            | 0.45                             | 0.20 |
| CWR29F^225^@A+□                | TAZ A 225 * 010 L □ # @ 0 ^ ++ | TAZ A 225 * 010 L □ L @ 9 ^ ++ | A  | 2.2                                 | 10                                 | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29F^225^@B+□                | TAZ B 225 * 010 L □ # @ 0 ^ ++ | TAZ B 225 * 010 L □ L @ 9 ^ ++ | B  | 2.2                                 | 10                                 | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29F^335^@A+□                | TAZ A 335 * 010 L □ # @ 0 ^ ++ | TAZ A 335 * 010 L □ L @ 9 ^ ++ | A  | 3.3                                 | 10                                 | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29F^335^@C+□                | TAZ C 335 * 010 L □ # @ 0 ^ ++ | TAZ C 335 * 010 L □ L @ 9 ^ ++ | C  | 3.3                                 | 10                                 | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |
| CWR29F^475^@B+□                | TAZ B 475 * 010 L □ # @ 0 ^ ++ | TAZ B 475 * 010 L □ L @ 9 ^ ++ | B  | 4.7                                 | 10                                 | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29F^475^@C+□                | TAZ C 475 * 010 L □ # @ 0 ^ ++ | TAZ C 475 * 010 L □ L @ 9 ^ ++ | C  | 4.7                                 | 10                                 | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# TAZ Series



## CWR29 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                | Parametric Specifications by Rating per MIL-PRF-55365/11 |                                     |                                    |         |       |       |        |       |       | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|--------------------------------|--------------------------------|--|-------------------------------------|------------------------------------|---------|-------|-------|--------|-------|-------|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                                |                                | Cap<br>@ 120Hz<br>µF<br>@ 25°C                           | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |       |       | DF Max |       |       | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
| CWR29 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case   | +25°C                               | +85°C                              | +125°C  | +25°C | +85°C | +125°C | +25°C | +85°C | +125°C                            | W                               | A                               | A                                | A                               | V                               | V                                | V    |
| CWR29F^475^@D+□                | TAZ D 475 * 010 L □ # @ 0 ^ ++ | TAZ D 475 * 010 L □ L @ 9 ^ ++ | D  | 4.7                                 | 10                                 | 1.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.23                            | 0.21                             | 0.09                            | 0.35                            | 0.31                             | 0.14 |
| CWR29F^685^@B+□                | TAZ B 685 * 010 L □ # @ 0 ^ ++ | TAZ B 685 * 010 L □ L @ 9 ^ ++ | B  | 6.8                                 | 10                                 | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29F^685^@C+□                | TAZ C 685 * 010 L □ # @ 0 ^ ++ | TAZ C 685 * 010 L □ L @ 9 ^ ++ | C  | 6.8                                 | 10                                 | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |
| CWR29F^685^@D+□                | TAZ D 685 * 010 L □ # @ 0 ^ ++ | TAZ D 685 * 010 L □ L @ 9 ^ ++ | D  | 6.8                                 | 10                                 | 1.7     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.22                            | 0.20                             | 0.09                            | 0.37                            | 0.33                             | 0.15 |
| CWR29F^685^@E+□                | TAZ E 685 * 010 L □ # @ 0 ^ ++ | TAZ E 685 * 010 L □ L @ 9 ^ ++ | E  | 6.8                                 | 10                                 | 1       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.090                           | 0.30                            | 0.27                             | 0.12                            | 0.30                            | 0.27                             | 0.12 |
| CWR29F^106^@B+□                | TAZ B 106 * 010 L □ # @ 0 ^ ++ | TAZ B 106 * 010 L □ L @ 9 ^ ++ | B  | 10                                  | 10                                 | 3.2     | 1     | 10    | 12     | 8     | 10    | 10                                | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29F^106^@C+□                | TAZ C 106 * 010 L □ # @ 0 ^ ++ | TAZ C 106 * 010 L □ L @ 9 ^ ++ | C  | 10                                  | 10                                 | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |
| CWR29F^106^@D+□                | TAZ D 106 * 010 L □ # @ 0 ^ ++ | TAZ D 106 * 010 L □ L @ 9 ^ ++ | D  | 10                                  | 10                                 | 1.3     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.25                            | 0.22                             | 0.10                            | 0.32                            | 0.29                             | 0.13 |
| CWR29F^106^@E+□                | TAZ E 106 * 010 L □ # @ 0 ^ ++ | TAZ E 106 * 010 L □ L @ 9 ^ ++ | E  | 10                                  | 10                                 | 1       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.090                           | 0.30                            | 0.27                             | 0.12                            | 0.30                            | 0.27                             | 0.12 |
| CWR29F^156^@D+□                | TAZ D 156 * 010 L □ # @ 0 ^ ++ | TAZ D 156 * 010 L □ L @ 9 ^ ++ | D  | 15                                  | 10                                 | 1.7     | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.080                           | 0.22                            | 0.20                             | 0.09                            | 0.37                            | 0.33                             | 0.15 |
| CWR29F^156^@E+□                | TAZ E 156 * 010 L □ # @ 0 ^ ++ | TAZ E 156 * 010 L □ L @ 9 ^ ++ | E  | 15                                  | 10                                 | 0.9     | 2     | 20    | 24     | 6     | 10    | 10                                | 0.090                           | 0.32                            | 0.28                             | 0.13                            | 0.28                            | 0.26                             | 0.11 |
| CWR29F^156^@F+□                | TAZ F 156 * 010 L □ # @ 0 ^ ++ | TAZ F 156 * 010 L □ L @ 9 ^ ++ | F  | 15                                  | 10                                 | 0.7     | 2     | 20    | 24     | 8     | 8     | 10                                | 0.100                           | 0.38                            | 0.34                             | 0.15                            | 0.26                            | 0.24                             | 0.11 |
| CWR29F^226^@E+□                | TAZ E 226 * 010 L □ # @ 0 ^ ++ | TAZ E 226 * 010 L □ L @ 9 ^ ++ | E  | 22                                  | 10                                 | 0.6     | 3     | 30    | 36     | 8     | 10    | 10                                | 0.090                           | 0.39                            | 0.35                             | 0.15                            | 0.23                            | 0.21                             | 0.09 |
| CWR29F^336^@F+□                | TAZ F 336 * 010 L □ # @ 0 ^ ++ | TAZ F 336 * 010 L □ L @ 9 ^ ++ | F  | 33                                  | 10                                 | 0.4     | 3     | 30    | 36     | 8     | 10    | 10                                | 0.100                           | 0.50                            | 0.45                             | 0.20                            | 0.20                            | 0.18                             | 0.08 |
| CWR29F^336^@G+□                | TAZ G 336 * 010 L □ # @ 0 ^ ++ | TAZ G 336 * 010 L □ L @ 9 ^ ++ | G  | 33                                  | 10                                 | 0.275   | 3     | 30    | 36     | 10    | 12    | 12                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29F^476^@F+□                | TAZ F 476 * 010 L □ # @ 0 ^ ++ | TAZ F 476 * 010 L □ L @ 9 ^ ++ | F  | 47                                  | 10                                 | 0.4     | 4     | 40    | 48     | 10    | 12    | 12                                | 0.100                           | 0.50                            | 0.45                             | 0.20                            | 0.20                            | 0.18                             | 0.08 |
| CWR29F^476^@G+□                | TAZ G 476 * 010 L □ # @ 0 ^ ++ | TAZ G 476 * 010 L □ L @ 9 ^ ++ | G  | 47                                  | 10                                 | 0.25    | 4     | 40    | 48     | 10    | 12    | 12                                | 0.125                           | 0.71                            | 0.64                             | 0.28                            | 0.18                            | 0.16                             | 0.07 |
| CWR29F^476^@H+□                | TAZ H 476 * 010 L □ # @ 0 ^ ++ | TAZ H 476 * 010 L □ L @ 9 ^ ++ | H  | 47                                  | 10                                 | 0.18    | 5     | 50    | 60     | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29F^686^@G+□                | TAZ G 686 * 010 L □ # @ 0 ^ ++ | TAZ G 686 * 010 L □ L @ 9 ^ ++ | G  | 68                                  | 10                                 | 0.275   | 6     | 60    | 72     | 10    | 12    | 12                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29F^107^@G+□                | TAZ G 107 * 010 L □ # @ 0 ^ ++ | TAZ G 107 * 010 L □ L @ 9 ^ ++ | G  | 100                                 | 10                                 | 0.275   | 10    | 100   | 120    | 10    | 12    | 12                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29F^107^@H+□                | TAZ H 107 * 010 L □ # @ 0 ^ ++ | TAZ H 107 * 010 L □ L @ 9 ^ ++ | H  | 100                                 | 10                                 | 0.18    | 10    | 100   | 120    | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29F^157^@H+□                | TAZ H 157 * 010 L □ # @ 0 ^ ++ | TAZ H 157 * 010 L □ L @ 9 ^ ++ | H  | 150                                 | 10                                 | 0.18    | 15    | 150   | 180    | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29F^157^@X+□                | TAZ X 157 * 010 L □ # @ 0 ^ ++ | TAZ X 157 * 010 L □ L @ 9 ^ ++ | X  | 150                                 | 10                                 | 0.065   | 15    | 150   | 180    | 10    | 12    | 12                                | 0.200                           | 1.75                            | 1.58                             | 0.70                            | 0.11                            | 0.10                             | 0.05 |
| CWR29F^227^@H+□                | TAZ H 227 * 010 L □ # @ 0 ^ ++ | TAZ H 227 * 010 L □ L @ 9 ^ ++ | H  | 220                                 | 10                                 | 0.18    | 20    | 200   | 240    | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29H^684^@A+□                | TAZ A 684 * 015 L □ # @ 0 ^ ++ | TAZ A 684 * 015 L □ L @ 9 ^ ++ | A  | 0.68                                | 15                                 | 6       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.09                            | 0.08                             | 0.04                            | 0.55                            | 0.49                             | 0.22 |
| CWR29H^105^@A+□                | TAZ A 105 * 015 L □ # @ 0 ^ ++ | TAZ A 105 * 015 L □ L @ 9 ^ ++ | A  | 1                                   | 15                                 | 7.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |
| CWR29H^155^@A+□                | TAZ A 155 * 015 L □ # @ 0 ^ ++ | TAZ A 155 * 015 L □ L @ 9 ^ ++ | A  | 1.5                                 | 15                                 | 7.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |
| CWR29H^155^@B+□                | TAZ B 155 * 015 L □ # @ 0 ^ ++ | TAZ B 155 * 015 L □ L @ 9 ^ ++ | B  | 1.5                                 | 15                                 | 3.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.15                            | 0.13                             | 0.06                            | 0.47                            | 0.43                             | 0.19 |
| CWR29H^225^@A+□                | TAZ A 225 * 015 L □ # @ 0 ^ ++ | TAZ A 225 * 015 L □ L @ 9 ^ ++ | A  | 2.2                                 | 15                                 | 7.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |
| CWR29H^225^@C+□                | TAZ C 225 * 015 L □ # @ 0 ^ ++ | TAZ C 225 * 015 L □ L @ 9 ^ ++ | C  | 2.2                                 | 15                                 | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |
| CWR29H^335^@B+□                | TAZ B 335 * 015 L □ # @ 0 ^ ++ | TAZ B 335 * 015 L □ L @ 9 ^ ++ | B  | 3.3                                 | 15                                 | 3.6     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.14                            | 0.13                             | 0.06                            | 0.50                            | 0.45                             | 0.20 |
| CWR29H^335^@D+□                | TAZ D 335 * 015 L □ # @ 0 ^ ++ | TAZ D 335 * 015 L □ L @ 9 ^ ++ | D  | 3.3                                 | 15                                 | 1.7     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.22                            | 0.20                             | 0.09                            | 0.37                            | 0.33                             | 0.15 |
| CWR29H^475^@B+□                | TAZ B 475 * 015 L □ # @ 0 ^ ++ | TAZ B 475 * 015 L □ L @ 9 ^ ++ | B  | 4.7                                 | 15                                 | 2       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.070                           | 0.19                            | 0.17                             | 0.07                            | 0.37                            | 0.34                             | 0.15 |
| CWR29H^475^@C+□                | TAZ C 475 * 015 L □ # @ 0 ^ ++ | TAZ C 475 * 015 L □ L @ 9 ^ ++ | C  | 4.7                                 | 15                                 | 2.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.075                           | 0.18                            | 0.17                             | 0.07                            | 0.41                            | 0.37                             | 0.16 |
| CWR29H^475^@D+□                | TAZ D 475 * 015 L □ # @ 0 ^ ++ | TAZ D 475 * 015 L □ L @ 9 ^ ++ | D  | 4.7                                 | 15                                 | 2       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.20                            | 0.18                             | 0.08                            | 0.40                            | 0.36                             | 0.16 |
| CWR29H^475^@E+□                | TAZ E 475 * 015 L □ # @ 0 ^ ++ | TAZ E 475 * 015 L □ L @ 9 ^ ++ | E  | 4.7                                 | 15                                 | 1.2     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.090                           | 0.27                            | 0.25                             | 0.11                            | 0.33                            | 0.30                             | 0.13 |
| CWR29H^685^@D+□                | TAZ D 685 * 015 L □ # @ 0 ^ ++ | TAZ D 685 * 015 L □ L @ 9 ^ ++ | D  | 6.8                                 | 15                                 | 2       | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.080                           | 0.20                            | 0.18                             | 0.08                            | 0.40                            | 0.36                             | 0.16 |
| CWR29H^685^@E+□                | TAZ E 685 * 015 L □ # @ 0 ^ ++ | TAZ E 685 * 015 L □ L @ 9 ^ ++ | E  | 6.8                                 | 15                                 | 0.9     | 1     | 10    | 12     | 8     | 10    | 12                                | 0.090                           | 0.32                            | 0.28                             | 0.13                            | 0.28                            | 0.26                             | 0.11 |
| CWR29H^106^@D+□                | TAZ D 106 * 015 L □ # @ 0 ^ ++ | TAZ D 106 * 015 L □ L @ 9 ^ ++ | D  | 10                                  | 15                                 | 2       | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.080                           | 0.20                            | 0.18                             | 0.08                            | 0.40                            | 0.36                             | 0.16 |
| CWR29H^106^@E+□                | TAZ E 106 * 015 L □ # @ 0 ^ ++ | TAZ E 106 * 015 L □ L @ 9 ^ ++ | E  | 10                                  | 15                                 | 1.2     | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.090                           | 0.27                            | 0.25                             | 0.11                            | 0.33                            | 0.30                             | 0.13 |
| CWR29H^106^@F+□                | TAZ F 106 * 015 L □ # @ 0 ^ ++ | TAZ F 106 * 015 L □ L @ 9 ^ ++ | F  | 10                                  | 15                                 | 0.667   | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.100                           | 0.39                            | 0.35                             | 0.15                            | 0.26                            | 0.23                             | 0.10 |
| CWR29H^156^@E+□                | TAZ E 156 * 015 L □ # @ 0 ^ ++ | TAZ E 156 * 015 L □ L @ 9 ^ ++ | E  | 15                                  | 15                                 | 1.2     | 2     | 20    | 24     | 6     | 8     | 8                                 | 0.090                           | 0.27                            | 0.25                             | 0.11                            | 0.33                            | 0.30                             | 0.13 |
| CWR29H^156^@F+□                | TAZ F 156 * 015 L □ # @ 0 ^ ++ | TAZ F 156 * 015 L □ L @ 9 ^ ++ | F  | 15                                  | 15                                 | 0.8     | 2     | 20    | 24     | 8     | 10    | 10                                | 0.100                           | 0.35                            | 0.32                             | 0.14                            | 0.28                            | 0.25                             | 0.11 |
| CWR29H^226^@F+□                | TAZ F 226 * 015 L □ # @ 0 ^ ++ | TAZ F 226 * 015 L □ L @ 9 ^ ++ | F  | 22                                  | 15                                 | 0.8     | 3     | 30    | 36     | 8     | 10    | 10                                | 0.100                           | 0.35                            | 0.32                             | 0.14                            | 0.28                            | 0.25                             | 0.11 |
| CWR29H^226^@G+□                | TAZ G 226 * 015 L □ # @ 0 ^ ++ | TAZ G 226 * 015 L □ L @ 9 ^ ++ | G  | 22                                  | 15                                 | 0.275   | 4     | 40    | 48     | 6     | 8     | 8                                 | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29H^336^@F+□                | TAZ F 336 * 015 L □ # @ 0 ^ ++ | TAZ F 336 * 015 L □ L @ 9 ^ ++ | F  | 33                                  | 15                                 | 0.8     | 5     | 50    | 60     | 6     | 8     | 8                                 | 0.100                           | 0.35                            | 0.32                             | 0.14                            | 0.28                            | 0.25                             | 0.11 |
| CWR29H^336^@G+□                | TAZ G 336 * 015 L □ # @ 0 ^ ++ | TAZ G 336 * 015 L □ L @ 9 ^ ++ | G  | 33                                  | 15                                 | 0.275   | 6     | 60    | 72     | 8     | 10    | 10                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29H^336^@H+□                | TAZ H 336 * 015 L □ # @ 0 ^ ++ | TAZ H 336 * 015 L □ L @ 9 ^ ++ | H  | 33                                  | 15                                 | 0.18    | 5     | 50    | 60     | 8     | 10    | 10                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29H^476^@G+□                | TAZ G 476 * 015 L □ # @ 0 ^ ++ | TAZ G 476 * 015 L □ L @ 9 ^ ++ | G  | 47                                  | 15                                 | 0.275   | 10    | 100   | 120    | 8     | 10    | 10                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29H^476^@H+□                | TAZ H 476 * 015 L □ # @ 0 ^ ++ | TAZ H 476 * 015 L □ L @ 9 ^ ++ | H  | 47                                  | 15                                 | 0.18    | 10    | 100   | 120    | 8     | 10    | 10                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29H^686^@G+□                | TAZ G 686 * 015 L □ # @ 0 ^ ++ | TAZ G 686 * 015 L □ L @ 9 ^ ++ | G  | 68                                  | 15                                 | 0.275   | 10    | 100   | 120    | 8     | 10    | 10                                | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29H^686^@H+□                | TAZ H 686 * 015 L □ # @ 0 ^ ++ | TAZ H 686 * 015 L □ L @ 9 ^ ++ | H  | 68                                  | 15                                 | 0.18    | 10    | 100   | 120    | 8     | 10    | 10                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29H^107^@H+□                | TAZ H 107 * 015 L □ # @ 0 ^ ++ | TAZ H 107 * 015 L □ L @ 9 ^ ++ | H  | 100                                 | 15                                 | 0.18    | 15    | 150   | 180    | 10    | 12    | 12                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29J^474^@A+□                | TAZ A 474 * 020 L □ # @ 0 ^ ++ | TAZ A 474 * 020 L □ L @ 9 ^ ++ | A  | 0.47                                | 20                                 | 7.5     | 1     | 10    | 12     | 8     | 8     | 10                                | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |
| CWR29J^684^@A+□                | TAZ A 684 * 020 L □ # @ 0 ^ ++ | TAZ A 684 * 020 L □ L @ 9 ^ ++ | A  | 0.68                                | 20                                 | 7.5     | 1     | 10    | 12     | 6     | 8     | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# TAZ Series



## CWR29 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                | Parametric Specifications by Rating per MIL-PRF-55365/11 |                                     |                                    |         |       |           |        |    |    | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|--------------------------------|--------------------------------|--|-------------------------------------|------------------------------------|---------|-------|-----------|--------|----|----|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                                |                                | Cap<br>@ 120Hz<br>µF<br>@ 25°C                           | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |       |           | DF Max |    |    | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
| CWR29 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case   | +25°C                               | +85°C                              | +125°C  | +25°C | +85/125°C | -55°C  |    |    |                                   |                                 |                                 |                                  |                                 |                                 |                                  |      |
| CWR29J^684^@B+□                | TAZ B 684 * 020 L □ # @ 0 ^ ++ | TAZ B 684 * 020 L □ L @ 9 ^ ++ | B  | 0.68                                | 20                                 | 5.6     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.11                            | 0.10                             | 0.04                            | 0.63                            | 0.56                             | 0.25 |
| CWR29J^105^@A+□                | TAZ A 105 * 020 L □ # @ 0 ^ ++ | TAZ A 105 * 020 L □ L @ 9 ^ ++ | A  | 1                                   | 20                                 | 7.5     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |
| CWR29J^105^@B+□                | TAZ B 105 * 020 L □ # @ 0 ^ ++ | TAZ B 105 * 020 L □ L @ 9 ^ ++ | B  | 1                                   | 20                                 | 4.8     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.12                            | 0.11                             | 0.05                            | 0.58                            | 0.52                             | 0.23 |
| CWR29J^155^@B+□                | TAZ B 155 * 020 L □ # @ 0 ^ ++ | TAZ B 155 * 020 L □ L @ 9 ^ ++ | B  | 1.5                                 | 20                                 | 3.6     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.14                            | 0.13                             | 0.06                            | 0.50                            | 0.45                             | 0.20 |
| CWR29J^155^@C+□                | TAZ C 155 * 020 L □ # @ 0 ^ ++ | TAZ C 155 * 020 L □ L @ 9 ^ ++ | C  | 1.5                                 | 20                                 | 2.4     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.075                           | 0.18                            | 0.16                             | 0.07                            | 0.42                            | 0.38                             | 0.17 |
| CWR29J^225^@B+□                | TAZ B 225 * 020 L □ # @ 0 ^ ++ | TAZ B 225 * 020 L □ L @ 9 ^ ++ | B  | 2.2                                 | 20                                 | 3.6     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.14                            | 0.13                             | 0.06                            | 0.50                            | 0.45                             | 0.20 |
| CWR29J^225^@D+□                | TAZ D 225 * 020 L □ # @ 0 ^ ++ | TAZ D 225 * 020 L □ L @ 9 ^ ++ | D  | 2.2                                 | 20                                 | 1.7     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.22                            | 0.20                             | 0.09                            | 0.37                            | 0.33                             | 0.15 |
| CWR29J^335^@D+□                | TAZ D 335 * 020 L □ # @ 0 ^ ++ | TAZ D 335 * 020 L □ L @ 9 ^ ++ | D  | 3.3                                 | 20                                 | 2       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.20                            | 0.18                             | 0.08                            | 0.40                            | 0.36                             | 0.16 |
| CWR29J^335^@E+□                | TAZ E 335 * 020 L □ # @ 0 ^ ++ | TAZ E 335 * 020 L □ L @ 9 ^ ++ | E  | 3.3                                 | 20                                 | 1.2     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.090                           | 0.27                            | 0.25                             | 0.11                            | 0.33                            | 0.30                             | 0.13 |
| CWR29J^475^@E+□                | TAZ E 475 * 020 L □ # @ 0 ^ ++ | TAZ E 475 * 020 L □ L @ 9 ^ ++ | E  | 4.7                                 | 20                                 | 1.7     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.090                           | 0.23                            | 0.21                             | 0.09                            | 0.39                            | 0.35                             | 0.16 |
| CWR29J^685^@E+□                | TAZ E 685 * 020 L □ # @ 0 ^ ++ | TAZ E 685 * 020 L □ L @ 9 ^ ++ | E  | 6.8                                 | 20                                 | 1.5     | 2     | 685       | 20     | 24 | 6  | 8                                 | 0.090                           | 0.24                            | 0.22                             | 0.10                            | 0.37                            | 0.33                             | 0.15 |
| CWR29J^685^@F+□                | TAZ F 685 * 020 L □ # @ 0 ^ ++ | TAZ F 685 * 020 L □ L @ 9 ^ ++ | F  | 6.8                                 | 20                                 | 0.7     | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.100                           | 0.38                            | 0.34                             | 0.15                            | 0.26                            | 0.24                             | 0.11 |
| CWR29J^106^@E+□                | TAZ E 106 * 020 L □ # @ 0 ^ ++ | TAZ E 106 * 020 L □ L @ 9 ^ ++ | E  | 10                                  | 20                                 | 1.5     | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.090                           | 0.24                            | 0.22                             | 0.10                            | 0.37                            | 0.33                             | 0.15 |
| CWR29J^106^@F+□                | TAZ F 106 * 020 L □ # @ 0 ^ ++ | TAZ F 106 * 020 L □ L @ 9 ^ ++ | F  | 10                                  | 20                                 | 0.8     | 2     | 106       | 20     | 24 | 6  | 8                                 | 0.100                           | 0.35                            | 0.32                             | 0.14                            | 0.28                            | 0.25                             | 0.11 |
| CWR29J^156^@F+□                | TAZ F 156 * 020 L □ # @ 0 ^ ++ | TAZ F 156 * 020 L □ L @ 9 ^ ++ | F  | 15                                  | 20                                 | 0.8     | 3     | 30        | 36     | 6  | 8  | 8                                 | 0.100                           | 0.35                            | 0.32                             | 0.14                            | 0.28                            | 0.25                             | 0.11 |
| CWR29J^156^@G+□                | TAZ G 156 * 020 L □ # @ 0 ^ ++ | TAZ G 156 * 020 L □ L @ 9 ^ ++ | G  | 15                                  | 20                                 | 0.275   | 3     | 30        | 36     | 6  | 8  | 8                                 | 0.125                           | 0.67                            | 0.61                             | 0.27                            | 0.19                            | 0.17                             | 0.07 |
| CWR29J^226^@G+□                | TAZ G 226 * 020 L □ # @ 0 ^ ++ | TAZ G 226 * 020 L □ L @ 9 ^ ++ | G  | 22                                  | 20                                 | 0.625   | 4     | 40        | 48     | 6  | 8  | 8                                 | 0.125                           | 0.45                            | 0.40                             | 0.18                            | 0.28                            | 0.25                             | 0.11 |
| CWR29J^226^@H+□                | TAZ H 226 * 020 L □ # @ 0 ^ ++ | TAZ H 226 * 020 L □ L @ 9 ^ ++ | H  | 22                                  | 20                                 | 0.18    | 4     | 40        | 48     | 6  | 8  | 8                                 | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29J^336^@H+□                | TAZ H 336 * 020 L □ # @ 0 ^ ++ | TAZ H 336 * 020 L □ L @ 9 ^ ++ | H  | 33                                  | 20                                 | 0.18    | 6     | 60        | 72     | 6  | 8  | 10                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29J^476^@H+□                | TAZ H 476 * 020 L □ # @ 0 ^ ++ | TAZ H 476 * 020 L □ L @ 9 ^ ++ | H  | 47                                  | 20                                 | 0.18    | 10    | 100       | 120    | 8  | 10 | 10                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29J^476^@X+□                | TAZ X 476 * 020 L □ # @ 0 ^ ++ | TAZ X 476 * 020 L □ L @ 9 ^ ++ | X  | 47                                  | 20                                 | 0.11    | 10    | 100       | 120    | 8  | 10 | 10                                | 0.200                           | 1.35                            | 1.21                             | 0.54                            | 0.15                            | 0.13                             | 0.06 |
| CWR29K^334^@A+□                | TAZ A 334 * 025 L □ # @ 0 ^ ++ | TAZ A 334 * 025 L □ L @ 9 ^ ++ | A  | 0.33                                | 25                                 | 7.5     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |
| CWR29K^474^@A+□                | TAZ A 474 * 025 L □ # @ 0 ^ ++ | TAZ A 474 * 025 L □ L @ 9 ^ ++ | A  | 0.47                                | 25                                 | 7.5     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.08                            | 0.07                             | 0.03                            | 0.61                            | 0.55                             | 0.24 |
| CWR29K^684^@B+□                | TAZ B 684 * 025 L □ # @ 0 ^ ++ | TAZ B 684 * 025 L □ L @ 9 ^ ++ | B  | 0.68                                | 25                                 | 4       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.13                            | 0.12                             | 0.05                            | 0.53                            | 0.48                             | 0.21 |
| CWR29K^105^@B+□                | TAZ B 105 * 025 L □ # @ 0 ^ ++ | TAZ B 105 * 025 L □ L @ 9 ^ ++ | B  | 1                                   | 25                                 | 4       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.13                            | 0.12                             | 0.05                            | 0.53                            | 0.48                             | 0.21 |
| CWR29K^105^@C+□                | TAZ C 105 * 025 L □ # @ 0 ^ ++ | TAZ C 105 * 025 L □ L @ 9 ^ ++ | C  | 1                                   | 25                                 | 2.6     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.075                           | 0.17                            | 0.15                             | 0.07                            | 0.44                            | 0.40                             | 0.18 |
| CWR29K^155^@D+□                | TAZ D 155 * 025 L □ # @ 0 ^ ++ | TAZ D 155 * 025 L □ L @ 9 ^ ++ | D  | 1.5                                 | 25                                 | 1.7     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.22                            | 0.20                             | 0.09                            | 0.37                            | 0.33                             | 0.15 |
| CWR29K^225^@D+□                | TAZ D 225 * 025 L □ # @ 0 ^ ++ | TAZ D 225 * 025 L □ L @ 9 ^ ++ | D  | 2.2                                 | 25                                 | 2       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.20                            | 0.18                             | 0.08                            | 0.40                            | 0.36                             | 0.16 |
| CWR29K^225^@E+□                | TAZ E 225 * 025 L □ # @ 0 ^ ++ | TAZ E 225 * 025 L □ L @ 9 ^ ++ | E  | 2.2                                 | 25                                 | 1       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.090                           | 0.30                            | 0.27                             | 0.12                            | 0.30                            | 0.27                             | 0.12 |
| CWR29K^335^@E+□                | TAZ E 335 * 025 L □ # @ 0 ^ ++ | TAZ E 335 * 025 L □ L @ 9 ^ ++ | E  | 3.3                                 | 25                                 | 1.2     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.090                           | 0.27                            | 0.25                             | 0.11                            | 0.33                            | 0.30                             | 0.13 |
| CWR29K^475^@F+□                | TAZ F 475 * 025 L □ # @ 0 ^ ++ | TAZ F 475 * 025 L □ L @ 9 ^ ++ | F  | 4.7                                 | 25                                 | 0.7     | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.100                           | 0.38                            | 0.34                             | 0.15                            | 0.26                            | 0.24                             | 0.11 |
| CWR29K^685^@F+□                | TAZ F 685 * 025 L □ # @ 0 ^ ++ | TAZ F 685 * 025 L □ L @ 9 ^ ++ | F  | 6.8                                 | 25                                 | 0.8     | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.100                           | 0.35                            | 0.32                             | 0.14                            | 0.28                            | 0.25                             | 0.11 |
| CWR29K^685^@G+□                | TAZ G 685 * 025 L □ # @ 0 ^ ++ | TAZ G 685 * 025 L □ L @ 9 ^ ++ | G  | 6.8                                 | 25                                 | 0.3     | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.125                           | 0.65                            | 0.58                             | 0.26                            | 0.19                            | 0.17                             | 0.08 |
| CWR29K^106^@G+□                | TAZ G 106 * 025 L □ # @ 0 ^ ++ | TAZ G 106 * 025 L □ L @ 9 ^ ++ | G  | 10                                  | 25                                 | 0.35    | 3     | 30        | 36     | 6  | 8  | 8                                 | 0.125                           | 0.60                            | 0.54                             | 0.24                            | 0.21                            | 0.19                             | 0.08 |
| CWR29K^156^@G+□                | TAZ G 156 * 025 L □ # @ 0 ^ ++ | TAZ G 156 * 025 L □ L @ 9 ^ ++ | G  | 15                                  | 25                                 | 0.35    | 4     | 40        | 48     | 6  | 8  | 8                                 | 0.125                           | 0.60                            | 0.54                             | 0.24                            | 0.21                            | 0.19                             | 0.08 |
| CWR29K^156^@H+□                | TAZ H 156 * 025 L □ # @ 0 ^ ++ | TAZ H 156 * 025 L □ L @ 9 ^ ++ | H  | 15                                  | 25                                 | 0.2     | 4     | 40        | 48     | 6  | 8  | 8                                 | 0.150                           | 0.87                            | 0.78                             | 0.35                            | 0.17                            | 0.16                             | 0.07 |
| CWR29K^226^@G+□                | TAZ G 226 * 025 L □ # @ 0 ^ ++ | TAZ G 226 * 025 L □ L @ 9 ^ ++ | G  | 22                                  | 25                                 | 0.35    | 6     | 60        | 72     | 6  | 8  | 8                                 | 0.125                           | 0.60                            | 0.54                             | 0.24                            | 0.21                            | 0.19                             | 0.08 |
| CWR29K^226^@H+□                | TAZ H 226 * 025 L □ # @ 0 ^ ++ | TAZ H 226 * 025 L □ L @ 9 ^ ++ | H  | 22                                  | 25                                 | 0.18    | 6     | 60        | 72     | 6  | 8  | 8                                 | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29K^336^@H+□                | TAZ H 336 * 025 L □ # @ 0 ^ ++ | TAZ H 336 * 025 L □ L @ 9 ^ ++ | H  | 33                                  | 25                                 | 0.18    | 10    | 100       | 120    | 8  | 10 | 10                                | 0.150                           | 0.91                            | 0.82                             | 0.37                            | 0.16                            | 0.15                             | 0.07 |
| CWR29M^224^@A+□                | TAZ A 224 * 035 L □ # @ 0 ^ ++ | TAZ A 224 * 035 L □ L @ 9 ^ ++ | A  | 0.22                                | 35                                 | 12      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR29M^334^@A+□                | TAZ A 334 * 035 L □ # @ 0 ^ ++ | TAZ A 334 * 035 L □ L @ 9 ^ ++ | A  | 0.33                                | 35                                 | 12      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR29M^474^@B+□                | TAZ B 474 * 035 L □ # @ 0 ^ ++ | TAZ B 474 * 035 L □ L @ 9 ^ ++ | B  | 0.47                                | 35                                 | 6.8     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.070                           | 0.10                            | 0.09                             | 0.04                            | 0.69                            | 0.62                             | 0.28 |
| CWR29M^684^@C+□                | TAZ C 684 * 035 L □ # @ 0 ^ ++ | TAZ C 684 * 035 L □ L @ 9 ^ ++ | C  | 0.68                                | 35                                 | 4       | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.075                           | 0.14                            | 0.12                             | 0.05                            | 0.55                            | 0.49                             | 0.22 |
| CWR29M^105^@D+□                | TAZ D 105 * 035 L □ # @ 0 ^ ++ | TAZ D 105 * 035 L □ L @ 9 ^ ++ | D  | 1                                   | 35                                 | 2.2     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.080                           | 0.19                            | 0.17                             | 0.08                            | 0.42                            | 0.38                             | 0.17 |
| CWR29M^155^@E+□                | TAZ E 155 * 035 L □ # @ 0 ^ ++ | TAZ E 155 * 035 L □ L @ 9 ^ ++ | E  | 1.5                                 | 35                                 | 1.3     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.090                           | 0.26                            | 0.24                             | 0.11                            | 0.34                            | 0.31                             | 0.14 |
| CWR29M^335^@F+□                | TAZ F 335 * 035 L □ # @ 0 ^ ++ | TAZ F 335 * 035 L □ L @ 9 ^ ++ | F  | 3.3                                 | 35                                 | 0.7     | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.100                           | 0.38                            | 0.34                             | 0.15                            | 0.26                            | 0.24                             | 0.11 |
| CWR29M^475^@G+□                | TAZ G 475 * 035 L □ # @ 0 ^ ++ | TAZ G 475 * 035 L □ L @ 9 ^ ++ | G  | 4.7                                 | 35                                 | 0.375   | 2     | 20        | 24     | 6  | 8  | 8                                 | 0.125                           | 0.58                            | 0.52                             | 0.23                            | 0.22                            | 0.19                             | 0.09 |
| CWR29M^685^@G+□                | TAZ G 685 * 035 L □ # @ 0 ^ ++ | TAZ G 685 * 035 L □ L @ 9 ^ ++ | G  | 6.8                                 | 35                                 | 0.375   | 3     | 30        | 36     | 6  | 8  | 8                                 | 0.125                           | 0.58                            | 0.52                             | 0.23                            | 0.22                            | 0.19                             | 0.09 |
| CWR29M^685^@H+□                | TAZ H 685 * 035 L □ # @ 0 ^ ++ | TAZ H 685 * 035 L □ L @ 9 ^ ++ | H  | 6.8                                 | 35                                 | 0.5     | 3     | 30        | 36     | 6  | 8  | 8                                 | 0.150                           | 0.55                            | 0.49                             | 0.22                            | 0.27                            | 0.25                             | 0.11 |
| CWR29M^106^@H+□                | TAZ H 106 * 035 L □ # @ 0 ^ ++ | TAZ H 106 * 035 L □ L @ 9 ^ ++ | H  | 10                                  | 35                                 | 0.5     | 4     | 40        | 48     | 8  | 10 | 10                                | 0.150                           | 0.55                            | 0.49                             | 0.22                            | 0.27                            | 0.25                             | 0.11 |
| CWR29M^156^@X+□                | TAZ X 156 * 035 L □ # @ 0 ^ ++ | TAZ X 156 * 035 L □ L @ 9 ^ ++ | X  | 15                                  | 35                                 | 0.19    | 6     | 60        | 72     | 6  | 8  | 8                                 | 0.200                           | 1.03                            | 0.92                             | 0.41                            | 0.19                            | 0.18                             | 0.08 |
| CWR29N^104^@A+□                | TAZ A 104 * 050 L □ # @ 0 ^ ++ | TAZ A 104 * 050 L □ L @ 9 ^ ++ | A  | 0.1                                 | 50                                 | 12      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |
| CWR29N^154^@A+□                | TAZ A 154 * 050 L □ # @ 0 ^ ++ | TAZ A 154 * 050 L □ L @ 9 ^ ++ | A  | 0.15                                | 50                                 | 12      | 1     | 10        | 12     | 6  | 8  | 8                                 | 0.050                           | 0.06                            | 0.06                             | 0.03                            | 0.77                            | 0.70                             | 0.31 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TAZ Series



## CWR29 - MIL-PRF-55365/11 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                |      | Parametric Specifications by Rating per MIL-PRF-55365/11 |                                     |                                    |                          |               |                |              |              | Typical RMS Ripple Data by Rating |              |                           |                                 |                                 |                                  |                                 |                                 |
|--------------------------------|--------------------------------|--------------------------------|------|--|-------------------------------------|------------------------------------|--------------------------|---------------|----------------|--------------|--------------|-----------------------------------|--------------|---------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|
|                                |                                |                                |      | Cap<br>@ 120Hz<br>μF<br>@ 25°C                           | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max<br>+25°C<br>(μA) | +85°C<br>(μA) | +125°C<br>(μA) | +25°C<br>(%) | +25°C<br>(%) | DF Max<br>+(85/125)°C<br>(%)      | -55°C<br>(%) | Power<br>Dissipation<br>W | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) |
| CWR29 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case |  |                                     |                                    |                          |               |                |              |              |                                   |              |                           |                                 |                                 |                                  |                                 |                                 |
| CWR29N^224^@B+□                | TAZ B 224 * 050 L □ # @ 0 ^ ++ | TAZ B 224 * 050 L □ L @ 9 ^ ++ | B    | 0.22   | 50                                  | 6.8                                | 1                        | 10            | 12             | 6            | 8            | 8                                 | 0.070        | 0.10                      | 0.09                            | 0.04                            | 0.69                             | 0.62                            | 0.28                            |
| CWR29N^334^@B+□                | TAZ B 334 * 050 L □ # @ 0 ^ ++ | TAZ B 334 * 050 L □ L @ 9 ^ ++ | B    | 0.33   | 50                                  | 4.8                                | 1                        | 10            | 12             | 6            | 8            | 8                                 | 0.070        | 0.12                      | 0.11                            | 0.05                            | 0.58                             | 0.52                            | 0.23                            |
| CWR29N^474^@C+□                | TAZ C 474 * 050 L □ # @ 0 ^ ++ | TAZ C 474 * 050 L □ L @ 9 ^ ++ | C    | 0.47   | 50                                  | 3.2                                | 1                        | 10            | 12             | 6            | 8            | 8                                 | 0.075        | 0.15                      | 0.14                            | 0.06                            | 0.49                             | 0.44                            | 0.20                            |
| CWR29N^684^@D+□                | TAZ D 684 * 050 L □ # @ 0 ^ ++ | TAZ D 684 * 050 L □ L @ 9 ^ ++ | D    | 0.68   | 50                                  | 2.3                                | 1                        | 10            | 12             | 6            | 8            | 8                                 | 0.080        | 0.19                      | 0.17                            | 0.07                            | 0.43                             | 0.39                            | 0.17                            |
| CWR29N^105^@E+□                | TAZ E 105 * 050 L □ # @ 0 ^ ++ | TAZ E 105 * 050 L □ L @ 9 ^ ++ | E    | 1  | 50                                  | 1.7                                | 1                        | 10            | 12             | 6            | 8            | 8                                 | 0.090        | 0.23                      | 0.21                            | 0.09                            | 0.39                             | 0.35                            | 0.16                            |
| CWR29N^155^@F+□                | TAZ F 155 * 050 L □ # @ 0 ^ ++ | TAZ F 155 * 050 L □ L @ 9 ^ ++ | F    | 1.5  | 50                                  | 1.1                                | 1                        | 10            | 12             | 6            | 8            | 8                                 | 0.100        | 0.30                      | 0.27                            | 0.12                            | 0.33                             | 0.30                            | 0.13                            |
| CWR29N^225^@F+□                | TAZ F 225 * 050 L □ # @ 0 ^ ++ | TAZ F 225 * 050 L □ L @ 9 ^ ++ | F    | 2.2  | 50                                  | 0.7                                | 2                        | 20            | 24             | 6            | 8            | 8                                 | 0.100        | 0.38                      | 0.34                            | 0.15                            | 0.26                             | 0.24                            | 0.11                            |
| CWR29N^335^@G+□                | TAZ G 335 * 050 L □ # @ 0 ^ ++ | TAZ G 335 * 050 L □ L @ 9 ^ ++ | G    | 3.3  | 50                                  | 0.5                                | 2                        | 20            | 24             | 6            | 8            | 8                                 | 0.125        | 0.50                      | 0.45                            | 0.20                            | 0.25                             | 0.23                            | 0.10                            |
| CWR29N^475^@H+□                | TAZ H 475 * 050 L □ # @ 0 ^ ++ | TAZ H 475 * 050 L □ L @ 9 ^ ++ | H    | 4.7  | 50                                  | 0.5                                | 3                        | 30            | 36             | 6            | 8            | 8                                 | 0.150        | 0.55                      | 0.49                            | 0.22                            | 0.27                             | 0.25                            | 0.11                            |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# TAZ Series



## HRC5000 Medical Implantable Grade




The TAZ HRC5000 Medical Grade series is designed for use in medical implantable applications. These are based off of the MIL-PRF-55365 case sizes and feature extremely low DC leakage levels well below typical values.

These components are manufactured and tested in the AVX Biddeford Maine factory which is ISO 13485 certified. Weibull grading and surge current testing options per MIL-PRF-55365 are

available along with several plating options including tin/lead solder, 100% tin, or gold terminations.

To request an additional rating not listed here, or for more information on HRC5000 testing details, please contact the factory.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.



### CASE DIMENSIONS:

millimeters (inches)

| Case Code | Length (L)<br>±0.38 (0.015) | Width (W)<br>±0.38 (0.015) | Height (H)<br>±0.38 (0.015) | Term. Width (W <sub>t</sub> )           | Term. Length (A)<br>+0.25/-0.13<br>(+0.010/-0.005) | S min        | Typical Weight (g) |
|-----------|-----------------------------|----------------------------|-----------------------------|---|--|--------------|--------------------|
| A         | 2.54 (0.100)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 0.38 (0.015) | 0.016              |
| B         | 3.81 (0.150)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 1.65 (0.065) | 0.025              |
| C         | 5.08 (0.200)                | 1.27 (0.050)               | 1.27 (0.050)                | 1.27±0.13<br>(0.050±0.005)              | 0.76 (0.030)                                       | 2.92 (0.115) | 0.035              |
| D         | 3.81 (0.150)                | 2.54 (0.100)               | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 1.65 (0.065) | 0.045              |
| E         | 5.08 (0.200)                | 2.54 (0.100)               | 1.27 (0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76 (0.030)                                       | 2.92 (0.115) | 0.065              |
| F         | 5.59 (0.220)                | 3.43 (0.135)               | 1.78 (0.070)                | 3.30±0.13<br>(0.130±0.005)              | 0.76 (0.030)                                       | 3.43 (0.135) | 0.125              |
| G         | 6.73 (0.265)                | 2.79 (0.110)               | 2.79 (0.110)                | 2.67±0.13<br>(0.105±0.005)              | 1.27 (0.050)                                       | 3.56 (0.140) | 0.205              |
| H         | 7.24 (0.285)                | 3.81 (0.150)               | 2.79 (0.110)                | 3.68+0.13/-0.51<br>(0.145+0.005/-0.020) | 1.27 (0.050)                                       | 4.06 (0.160) | 0.335              |

### MARKING

(White marking on black body)



Polarity Stripe (+)

Capacitance Code  
Rated Voltage

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage |         |       |     |       |     |     |     |     |
|-------------|------|---------------|---------|-------|-----|-------|-----|-----|-----|-----|
| µF          | Code | 4V            | 6V      | 10V   | 12V | 15V   | 20V | 25V | 35V | 50V |
| 0.10        | 104  |               |         |       |     |       |     |     |     | A   |
| 0.15        | 154  |               |         |       |     |       |     |     |     | A   |
| 0.22        | 224  |               |         |       |     |       |     |     | A   |     |
| 0.33        | 334  |               |         |       |     |       |     | A   | B   |     |
| 0.47        | 474  |               |         |       |     |       | A   |     |     |     |
| 0.68        | 684  |               |         |       |     | A     |     |     |     |     |
| 1           | 105  |               |         | A     |     | A     | A/B | B   | D   | E   |
| 1.5         | 155  |               | A       | A     |     | B     | D   |     |     |     |
| 2.2         | 225  | A             | A       | A/B   |     | A/B/C | B/D | D/E |     | F   |
| 3.3         | 335  |               | A/B     | A/B   |     | B/D   | E   | E   | F   | G   |
| 4.7         | 475  | A/B           | A       | B/D   |     | B/D/E | D/E | F   |     |     |
| 6           | 605  |               |         |       |     |       |     |     |     |     |
| 6.8         | 685  | A             | D       | B/D/E |     | D/E/F | D/E | F   |     |     |
| 10          | 106  | D             | B/D/E   | B/D/E |     | D/E/F | E   | G   | H   |     |
| 14          | 146  |               |         | E     |     |       |     |     |     |     |
| 15          | 156  |               | B/D/F   | D/E/F |     | E     | F/G | F/G |     |     |
| 22          | 226  |               | F       | D/E/F | E   | F/G   | G/H | H   |     |     |
| 33          | 336  | E/F           | E       | F/G   |     | F/H   |     |     |     |     |
| 47          | 476  | E             | E/F/G   | F/G/H |     | G     | H   |     |     |     |
| 68          | 686  | E/G           | E/F/G/H | G     |     |       |     |     |     |     |
| 100         | 107  | F             | G       | H     |     | H     |     |     |     |     |
| 150         | 157  |               | G       | H     |     |       |     |     |     |     |
| 220         | 227  |               |         | H     |     |       |     |     |     |     |
| 300         | 307  |               | H       |       |     |       |     |     |     |     |
| 330         | 337  |               | H       |       |     |       |     |     |     |     |







# TAZ Series



## HRC5000 Medical Implantable Grade

### HOW TO ORDER

|             |                  |  |                                 |  |                            |                                      |                         |   |                            |  |   |
|-------------|------------------|--|---------------------------------|--|----------------------------|--------------------------------------|-------------------------|---|----------------------------|--|---|
| <b>TAZ</b>  | <b>E</b>         | <b>106</b>   | <b>*</b>                        | <b>010</b>   | <b>C</b>                   | <b>□</b>                             | <b>L</b>                | <b>@</b>  | <b>5</b>                   | <b>^</b>   | <b>++</b>   |
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b>  | <b>Capacitance Tolerance</b>    | <b>Voltage Code</b>  | <b>ESR</b>                 | <b>Packaging</b>                     | <b>Inspection Level</b> | <b>Reliability Grade</b>  | <b>Qualification Level</b> | <b>Termination Finish</b>  | <b>Surge Test Option</b>  |
|             |                  | pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | J = ±5%<br>K = ±10%<br>M = ±20% | 004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | C = Std ESR<br>L = Low ESR | B = Bulk<br>R = 7* T&R<br>W = Waffle | L = Group A             | Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf. | 5 = HRC5000                | H = Solder Plated<br>0 = Solder Fused<br>9 = Gold Plated<br>7 = 100% Tin   | 00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 Cycles, -55°C & +85°C before Weibull |
|             |                  |  |                                 |  |                            |                                      |                         |   |                            | <br>LEAD-FREE<br>LEAD-FREE COMPATIBLE COMPONENT | <br>RoHS<br>COMPLIANT            |
|             |                  |  |                                 |  |                            |                                      |                         |   |                            | For RoHS compliant products, please select correct termination style.  |   |

\*Contact factory for AVX HRC5000 Medical Grade SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |     |      |      |      |      |      |      |  |
|------------------------------------|---|-----|-----|------|------|------|------|------|------|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |     |      |      |      |      |      |      |  |
| Capacitance Range:                 | 0.10 µF to 330 µF   |     |     |      |      |      |      |      |      |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |     |      |      |      |      |      |      |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6   | 10   | 15   | 20   | 25   | 35   | 50   |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4   | 6.7  | 10   | 13.3 | 16.7 | 23.3 | 33.3 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 5.3 | 8   | 13.3 | 20   | 26.7 | 33.3 | 46.7 | 66.7 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 3.5 | 5.3 | 8.7  | 13.3 | 17.8 | 22.2 | 31.1 | 44.5 |  |
| Temperature Range:                 | -55°C to +125°C   |     |     |      |      |      |      |      |      |  |

# TAZ Series

## HRC5000 Medical Implantable Grade



| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating |                  |              |         |        |        |        |             |       | Typical RMS Ripple Data by Rating |                     |                     |                      |                     |                     |                      |
|--------------------------------|------|-------------------------------------|------------------|--------------|---------|--------|--------|--------|-------------|-------|-----------------------------------|---------------------|---------------------|----------------------|---------------------|---------------------|----------------------|
|                                |      | Cap @ 120Hz                         | DC Rated Voltage | ESR @ 100kHz | DCL max |        |        | DF max |             |       | Power Dissipation                 | 25°C Ripple Current | 85°C Ripple Current | 125°C Ripple Current | 25°C Ripple Voltage | 85°C Ripple Voltage | 125°C Ripple Voltage |
|                                |      |                                     |                  |              | +25°C   | +85°C  | +125°C | +25°C  | +(85/125)°C | -55°C |                                   |                     |                     |                      |                     |                     |                      |
| AVX P/N                        | Case | µF @ 25°C                           | V @ +85°C        | Ohms @ +25°C | (µA)    | (µA)   | (µA)   | (%)    | (%)         | (%)   | W                                 | A (100kHz)          | A (100kHz)          | A (100kHz)           | V (100kHz)          | V (100kHz)          | V (100kHz)           |
| TAZA225*004L□□@5^++            | A    | 2.2                                 | 4                | 4            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.112               | 0.101               | 0.045                | 0.447               | 0.402               | 0.179                |
| TAZA475*004L□□@5^++            | A    | 4.7                                 | 4                | 6            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.091               | 0.082               | 0.037                | 0.548               | 0.493               | 0.219                |
| TAZB475*004L□□@5^++            | B    | 4.7                                 | 4                | 3.2          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZA685*004L□□@5^++            | A    | 6.8                                 | 4                | 6            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.091               | 0.082               | 0.037                | 0.548               | 0.493               | 0.219                |
| TAZD106*004L□□@5^++            | D    | 10                                  | 4                | 1.3          | 0.100   | 1.000  | 1.200  | 8      | 8           | 10    | 0.080                             | 0.248               | 0.223               | 0.099                | 0.322               | 0.290               | 0.129                |
| TAZE336*004L□□@5^++            | E    | 33                                  | 4                | 0.9          | 0.330   | 3.300  | 3.960  | 8      | 10          | 12    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZF336*004L□□@5^++            | F    | 33                                  | 4                | 0.6          | 0.330   | 3.300  | 3.960  | 8      | 10          | 12    | 0.100                             | 0.408               | 0.367               | 0.163                | 0.245               | 0.220               | 0.098                |
| TAZE476*004L□□@5^++            | E    | 47                                  | 4                | 0.9          | 0.470   | 4.700  | 5.640  | 8      | 10          | 12    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZE686*004L□□@5^++            | E    | 68                                  | 4                | 0.9          | 0.680   | 6.800  | 8.160  | 8      | 10          | 12    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZG686*004L□□@5^++            | G    | 68                                  | 4                | 0.275        | 0.680   | 6.800  | 8.160  | 10     | 12          | 12    | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |
| TAZF107*004L□□@5^++            | F    | 100                                 | 4                | 0.55         | 1.000   | 10.000 | 12.000 | 10     | 12          | 12    | 0.100                             | 0.426               | 0.384               | 0.171                | 0.235               | 0.211               | 0.094                |
| TAZA155*006L□□@5^++            | A    | 1.5                                 | 6                | 4            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.112               | 0.101               | 0.045                | 0.447               | 0.402               | 0.179                |
| TAZA225*006C□□@5^++            | A    | 2.2                                 | 6                | 12           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.065               | 0.058               | 0.026                | 0.775               | 0.697               | 0.310                |
| TAZA335*006L□□@5^++            | A    | 3.3                                 | 6                | 6            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.091               | 0.082               | 0.037                | 0.548               | 0.493               | 0.219                |
| TAZB335*006L□□@5^++            | B    | 3.3                                 | 6                | 3.2          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZA475*006L□□@5^++            | A    | 4.7                                 | 6                | 6            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.091               | 0.082               | 0.037                | 0.548               | 0.493               | 0.219                |
| TAZD685*006L□□@5^++            | D    | 6.8                                 | 6                | 1.5          | 0.102   | 1.020  | 1.224  | 6      | 8           | 8     | 0.080                             | 0.231               | 0.208               | 0.092                | 0.346               | 0.312               | 0.139                |
| TAZB106*006L□□@5^++            | B    | 10                                  | 6                | 3.2          | 0.150   | 1.500  | 1.800  | 6      | 8           | 8     | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZD106*006C□□@5^++            | D    | 10                                  | 6                | 6            | 0.150   | 1.500  | 1.800  | 6      | 8           | 8     | 0.080                             | 0.115               | 0.104               | 0.046                | 0.693               | 0.624               | 0.277                |
| TAZE106*006L□□@5^++            | E    | 10                                  | 6                | 1            | 0.150   | 1.500  | 1.800  | 8      | 10          | 12    | 0.090                             | 0.300               | 0.270               | 0.120                | 0.300               | 0.270               | 0.120                |
| TAZB156*006L□□@5^++            | B    | 15                                  | 6                | 3.2          | 0.225   | 2.250  | 2.700  | 8      | 10          | 10    | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZD156*006L□□@5^++            | D    | 15                                  | 6                | 1.7          | 0.225   | 2.250  | 2.700  | 8      | 10          | 12    | 0.080                             | 0.217               | 0.195               | 0.087                | 0.369               | 0.332               | 0.148                |
| TAZF156*006C□□@5^++            | F    | 15                                  | 6                | 0.3          | 0.225   | 2.250  | 2.700  | 6      | 8           | 8     | 0.100                             | 0.577               | 0.520               | 0.231                | 0.173               | 0.156               | 0.069                |
| TAZF226*006L□□@5^++            | F    | 22                                  | 6                | 0.6          | 0.330   | 3.300  | 3.960  | 8      | 10          | 12    | 0.100                             | 0.408               | 0.367               | 0.163                | 0.245               | 0.220               | 0.098                |
| TAZE336*006L□□@5^++            | E    | 33                                  | 6                | 1            | 0.495   | 4.950  | 5.940  | 6      | 8           | 8     | 0.090                             | 0.300               | 0.270               | 0.120                | 0.300               | 0.270               | 0.120                |
| TAZE476*006C□□@5^++            | E    | 47                                  | 6                | 5            | 0.705   | 7.050  | 8.460  | 6      | 8           | 8     | 0.090                             | 0.134               | 0.121               | 0.054                | 0.671               | 0.604               | 0.268                |
| TAZF476*006L□□@5^++            | F    | 47                                  | 6                | 1            | 0.705   | 7.050  | 8.460  | 8      | 10          | 12    | 0.100                             | 0.316               | 0.285               | 0.126                | 0.316               | 0.285               | 0.126                |
| TAZG476*006L□□@5^++            | G    | 47                                  | 6                | 0.275        | 0.705   | 7.050  | 8.460  | 10     | 12          | 12    | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |
| TAZE686*006C□□@5^++            | E    | 68                                  | 6                | 2            | 1.020   | 10.200 | 12.240 | 10     | 12          | 12    | 0.090                             | 0.212               | 0.191               | 0.085                | 0.424               | 0.382               | 0.170                |
| TAZF686*006L□□@5^++            | F    | 68                                  | 6                | 0.4          | 1.020   | 10.200 | 12.240 | 10     | 12          | 12    | 0.100                             | 0.500               | 0.450               | 0.200                | 0.200               | 0.180               | 0.080                |
| TAZG686*006L□□@5^++            | G    | 68                                  | 6                | 0.25         | 1.020   | 10.200 | 12.240 | 10     | 12          | 12    | 0.125                             | 0.707               | 0.636               | 0.283                | 0.177               | 0.159               | 0.071                |
| TAZH686*006L□□@5^++            | H    | 68                                  | 6                | 0.18         | 1.020   | 10.200 | 12.240 | 10     | 12          | 12    | 0.150                             | 0.913               | 0.822               | 0.365                | 0.164               | 0.148               | 0.066                |
| TAZG107*006L□□@5^++            | G    | 100                                 | 6                | 0.275        | 1.500   | 15.000 | 18.000 | 10     | 12          | 12    | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |
| TAZG157*006L□□@5^++            | G    | 150                                 | 6                | 0.275        | 2.250   | 22.500 | 27.000 | 10     | 12          | 12    | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |
| TAZH307*006C□□@5^++            | H    | 300                                 | 6                | 0.9          | 4.500   | 45.000 | 54.000 | 15     | 18          | 18    | 0.150                             | 0.408               | 0.367               | 0.163                | 0.367               | 0.331               | 0.147                |
| TAZH337*006L□□@5^++            | H    | 330                                 | 6                | 0.18         | 4.950   | 49.500 | 59.400 | 10     | 12          | 12    | 0.150                             | 0.913               | 0.822               | 0.365                | 0.164               | 0.148               | 0.066                |
| TAZR334*010C□□@5^++            | R    | 0.33                                | 10               | 50           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.030                             | 0.024               | 0.022               | 0.010                | 1.225               | 1.102               | 0.490                |
| TAZA105*010L□□@5^++            | A    | 1                                   | 10               | 5            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.100               | 0.090               | 0.040                | 0.500               | 0.450               | 0.200                |
| TAZA155*010C□□@5^++            | A    | 1.5                                 | 10               | 12           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.065               | 0.058               | 0.026                | 0.775               | 0.697               | 0.310                |
| TAZA225*010L□□@5^++            | A    | 2.2                                 | 10               | 6            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.091               | 0.082               | 0.037                | 0.548               | 0.493               | 0.219                |
| TAZR225*010L□□@5^++            | B    | 2.2                                 | 10               | 3.2          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZA335*010L□□@5^++            | A    | 3.3                                 | 10               | 6            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.091               | 0.082               | 0.037                | 0.548               | 0.493               | 0.219                |
| TAZB335*010C□□@5^++            | B    | 3.3                                 | 10               | 18           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.062               | 0.056               | 0.025                | 1.122               | 1.010               | 0.449                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# TAZ Series

## HRC5000 Medical Implantable Grade



| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating |                  |              |         |        |        |        |             |       | Typical RMS Ripple Data by Rating |                     |                     |                      |                     |                     |                      |
|--------------------------------|------|-------------------------------------|------------------|--------------|---------|--------|--------|--------|-------------|-------|-----------------------------------|---------------------|---------------------|----------------------|---------------------|---------------------|----------------------|
|                                |      | Cap @ 120Hz                         | DC Rated Voltage | ESR @ 100kHz | DCL max |        |        | DF max |             |       | Power Dissipation                 | 25°C Ripple Current | 85°C Ripple Current | 125°C Ripple Current | 25°C Ripple Voltage | 85°C Ripple Voltage | 125°C Ripple Voltage |
|                                |      |                                     |                  |              | +25°C   | +85°C  | +125°C | +25°C  | +(85/125)°C | -55°C |                                   |                     |                     |                      |                     |                     |                      |
| AVX P/N                        | Case | µF @ 25°C                           | V @ +85°C        | Ohms @ +25°C | (µA)    | (µA)   | (µA)   | (%)    | (%)         | (%)   |                                   |                     |                     |                      |                     |                     |                      |
| TAZB475*010L□□@5^++            | B    | 4.7                                 | 10               | 3.2          | 0.200   | 2.000  | 2.400  | 6      | 8           | 8     | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZD475*010L□□@5^++            | D    | 4.7                                 | 10               | 1.5          | 0.200   | 2.000  | 2.400  | 6      | 8           | 8     | 0.080                             | 0.231               | 0.208               | 0.092                | 0.346               | 0.312               | 0.139                |
| TAZB685*010L□□@5^++            | B    | 6.8                                 | 10               | 3.2          | 0.170   | 1.700  | 2.040  | 6      | 8           | 8     | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZD685*010L□□@5^++            | D    | 6.8                                 | 10               | 1.7          | 0.170   | 1.700  | 2.040  | 6      | 8           | 8     | 0.080                             | 0.217               | 0.195               | 0.087                | 0.369               | 0.332               | 0.148                |
| TAZE685*010L□□@5^++            | E    | 6.8                                 | 10               | 1            | 0.170   | 1.700  | 2.040  | 6      | 8           | 8     | 0.090                             | 0.300               | 0.270               | 0.120                | 0.300               | 0.270               | 0.120                |
| TAZB106*010L□□@5^++            | B    | 10                                  | 10               | 3.2          | 0.250   | 2.500  | 3.000  | 8      | 10          | 10    | 0.070                             | 0.148               | 0.133               | 0.059                | 0.473               | 0.426               | 0.189                |
| TAZD106*010L□□@5^++            | D    | 10                                  | 10               | 1.3          | 0.250   | 2.500  | 3.000  | 6      | 8           | 8     | 0.080                             | 0.248               | 0.223               | 0.099                | 0.322               | 0.290               | 0.129                |
| TAZE106*010L□□@5^++            | E    | 10                                  | 10               | 1            | 0.250   | 2.500  | 3.000  | 6      | 8           | 8     | 0.090                             | 0.300               | 0.270               | 0.120                | 0.300               | 0.270               | 0.120                |
| TAZE146*010C□□@5^++            | E    | 14                                  | 10               | 3            | 0.350   | 3.500  | 4.200  | 6      | 8           | 8     | 0.090                             | 0.173               | 0.156               | 0.069                | 0.520               | 0.468               | 0.208                |
| TAZD156*010L□□@5^++            | D    | 15                                  | 10               | 1.7          | 0.375   | 3.750  | 4.500  | 6      | 8           | 8     | 0.080                             | 0.217               | 0.195               | 0.087                | 0.369               | 0.332               | 0.148                |
| TAZE156*010L□□@5^++            | E    | 15                                  | 10               | 0.9          | 0.375   | 3.750  | 4.500  | 8      | 10          | 10    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZF156*010L□□@5^++            | F    | 15                                  | 10               | 0.7          | 0.375   | 3.750  | 4.500  | 8      | 8           | 10    | 0.100                             | 0.378               | 0.340               | 0.151                | 0.265               | 0.238               | 0.106                |
| TAZD226*010C□□@5^++            | D    | 22                                  | 10               | 8            | 0.550   | 5.500  | 6.600  | 6      | 8           | 8     | 0.080                             | 0.100               | 0.090               | 0.040                | 0.800               | 0.720               | 0.320                |
| TAZE226*010L□□@5^++            | E    | 22                                  | 10               | 0.6          | 0.550   | 5.500  | 6.600  | 8      | 10          | 10    | 0.090                             | 0.387               | 0.349               | 0.155                | 0.232               | 0.209               | 0.093                |
| TAZF226*010C□□@5^++            | F    | 22                                  | 10               | 3            | 0.550   | 5.500  | 6.600  | 8      | 10          | 10    | 0.100                             | 0.183               | 0.164               | 0.073                | 0.548               | 0.493               | 0.219                |
| TAZF336*010L□□@5^++            | F    | 33                                  | 10               | 0.4          | 0.825   | 8.250  | 9.900  | 8      | 10          | 10    | 0.100                             | 0.500               | 0.450               | 0.200                | 0.200               | 0.180               | 0.080                |
| TAZG336*010L□□@5^++            | G    | 33                                  | 10               | 0.275        | 0.825   | 8.250  | 9.900  | 10     | 12          | 12    | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |
| TAZF476*010L□□@5^++            | F    | 47                                  | 10               | 0.4          | 1.175   | 11.750 | 14.100 | 10     | 12          | 12    | 0.100                             | 0.500               | 0.450               | 0.200                | 0.200               | 0.180               | 0.080                |
| TAZG476*010L□□@5^++            | G    | 47                                  | 10               | 0.25         | 1.175   | 11.750 | 14.100 | 10     | 12          | 12    | 0.125                             | 0.707               | 0.636               | 0.283                | 0.177               | 0.159               | 0.071                |
| TAZH476*010L□□@5^++            | H    | 47                                  | 10               | 0.18         | 1.175   | 11.750 | 14.100 | 10     | 12          | 12    | 0.150                             | 0.913               | 0.822               | 0.365                | 0.164               | 0.148               | 0.066                |
| TAZG686*010L□□@5^++            | G    | 68                                  | 10               | 0.275        | 1.700   | 17.000 | 20.400 | 10     | 12          | 12    | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |
| TAZH107*010L□□@5^++            | H    | 100                                 | 10               | 0.18         | 2.500   | 25.000 | 30.000 | 10     | 12          | 12    | 0.150                             | 0.913               | 0.822               | 0.365                | 0.164               | 0.148               | 0.066                |
| TAZH157*010L□□@5^++            | H    | 150                                 | 10               | 0.18         | 3.750   | 37.500 | 45.000 | 10     | 12          | 12    | 0.150                             | 0.913               | 0.822               | 0.365                | 0.164               | 0.148               | 0.066                |
| TAZH227*010L□□@5^++            | H    | 220                                 | 10               | 0.18         | 5.500   | 55.000 | 66.000 | 10     | 12          | 12    | 0.150                             | 0.913               | 0.822               | 0.365                | 0.164               | 0.148               | 0.066                |
| TAZE226*012C□□@5^++            | E    | 22                                  | 12               | 0.5          | 0.660   | 6.600  | 7.920  | 6      | 8           | 8     | 0.090                             | 0.424               | 0.382               | 0.170                | 0.212               | 0.191               | 0.085                |
| TAZA684*015L□□@5^++            | A    | 0.68                                | 15               | 6            | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.091               | 0.082               | 0.037                | 0.548               | 0.493               | 0.219                |
| TAZA105*015L□□@5^++            | A    | 1                                   | 15               | 7.5          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.082               | 0.073               | 0.033                | 0.612               | 0.551               | 0.245                |
| TAZA225*015L□□@5^++            | A    | 2.2                                 | 15               | 7.5          | 0.200   | 2.000  | 2.400  | 6      | 8           | 8     | 0.050                             | 0.082               | 0.073               | 0.033                | 0.612               | 0.551               | 0.245                |
| TAZB225*015C□□@5^++            | B    | 2.2                                 | 15               | 5.5          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.113               | 0.102               | 0.045                | 0.620               | 0.558               | 0.248                |
| TAZB335*015L□□@5^++            | B    | 3.3                                 | 15               | 3.6          | 0.290   | 2.900  | 3.480  | 6      | 8           | 8     | 0.070                             | 0.139               | 0.125               | 0.056                | 0.502               | 0.452               | 0.201                |
| TAZD335*015L□□@5^++            | D    | 3.3                                 | 15               | 1.7          | 0.124   | 1.238  | 1.485  | 6      | 8           | 8     | 0.080                             | 0.217               | 0.195               | 0.087                | 0.369               | 0.332               | 0.148                |
| TAZB475*015L□□@5^++            | B    | 4.7                                 | 15               | 2            | 0.250   | 2.500  | 3.000  | 6      | 8           | 8     | 0.070                             | 0.187               | 0.168               | 0.075                | 0.374               | 0.337               | 0.150                |
| TAZD475*015L□□@5^++            | D    | 4.7                                 | 15               | 2            | 0.250   | 2.500  | 3.000  | 6      | 8           | 8     | 0.080                             | 0.200               | 0.180               | 0.080                | 0.400               | 0.360               | 0.160                |
| TAZE475*015L□□@5^++            | E    | 4.7                                 | 15               | 1.2          | 0.245   | 2.450  | 2.940  | 6      | 8           | 8     | 0.090                             | 0.274               | 0.246               | 0.110                | 0.329               | 0.296               | 0.131                |
| TAZD106*015L□□@5^++            | D    | 10                                  | 15               | 2            | 0.375   | 3.750  | 4.500  | 6      | 8           | 8     | 0.080                             | 0.200               | 0.180               | 0.080                | 0.400               | 0.360               | 0.160                |
| TAZE106*015L□□@5^++            | E    | 10                                  | 15               | 1.2          | 0.375   | 3.750  | 4.500  | 6      | 8           | 8     | 0.090                             | 0.274               | 0.246               | 0.110                | 0.329               | 0.296               | 0.131                |
| TAZF106*015L□□@5^++            | F    | 10                                  | 15               | 0.667        | 0.375   | 3.750  | 4.500  | 6      | 8           | 8     | 0.100                             | 0.387               | 0.348               | 0.155                | 0.258               | 0.232               | 0.103                |
| TAZE156*015L□□@5^++            | E    | 15                                  | 15               | 1.2          | 0.563   | 5.625  | 6.750  | 6      | 8           | 8     | 0.090                             | 0.274               | 0.246               | 0.110                | 0.329               | 0.296               | 0.131                |
| TAZF226*015L□□@5^++            | F    | 22                                  | 15               | 0.8          | 0.825   | 8.250  | 9.900  | 8      | 10          | 10    | 0.100                             | 0.354               | 0.318               | 0.141                | 0.283               | 0.255               | 0.113                |
| TAZG226*015L□□@5^++            | G    | 22                                  | 15               | 0.275        | 0.825   | 8.250  | 9.900  | 6      | 8           | 8     | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |
| TAZF336*015L□□@5^++            | F    | 33                                  | 15               | 0.8          | 1.238   | 12.375 | 14.850 | 6      | 8           | 8     | 0.100                             | 0.354               | 0.318               | 0.141                | 0.283               | 0.255               | 0.113                |
| TAZH336*015L□□@5^++            | H    | 33                                  | 15               | 0.18         | 1.238   | 12.375 | 14.850 | 8      | 8           | 10    | 0.150                             | 0.913               | 0.822               | 0.365                | 0.164               | 0.148               | 0.066                |
| TAZG476*015L□□@5^++            | G    | 47                                  | 15               | 0.275        | 1.763   | 17.625 | 21.150 | 8      | 10          | 10    | 0.125                             | 0.674               | 0.607               | 0.270                | 0.185               | 0.167               | 0.074                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# TAZ Series

## HRC5000 Medical Implantable Grade



| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating |                  |              |         |        |        |        |             |       | Typical RMS Ripple Data by Rating |                |                |                |                |                |                |
|--------------------------------|------|-------------------------------------|------------------|--------------|---------|--------|--------|--------|-------------|-------|-----------------------------------|----------------|----------------|----------------|----------------|----------------|----------------|
|                                |      | Cap @ 120Hz                         | DC Rated Voltage | ESR @ 100kHz | DCL max |        |        | DF max |             |       | Power Dissipation                 | 25°C           | 85°C           | 125°C          | 25°C           | 85°C           | 125°C          |
|                                |      |                                     |                  |              | +25°C   | +85°C  | +125°C | +25°C  | +(85/125)°C | -55°C |                                   | Ripple Current | Ripple Current | Ripple Current | Ripple Voltage | Ripple Voltage | Ripple Voltage |
| AVX P/N                        | Case | µF @ 25°C                           | V @ +85°C        | Ohms @ +25°C | (µA)    | (µA)   | (µA)   | (%)    | (%)         | (%)   | W                                 | A (100kHz)     | A (100kHz)     | A (100kHz)     | V (100kHz)     | V (100kHz)     | V (100kHz)     |
| TAZH107*015L□□@5^++            | H    | 100                                 | 15               | 0.18         | 3.750   | 37.500 | 45.000 | 10     | 12          | 12    | 0.150                             | 0.913          | 0.822          | 0.365          | 0.164          | 0.148          | 0.066          |
| TAZA474*020L□□@5^++            | A    | 0.47                                | 20               | 7.5          | 0.100   | 1.000  | 1.200  | 8      | 8           | 10    | 0.050                             | 0.082          | 0.073          | 0.033          | 0.612          | 0.551          | 0.245          |
| TAZA105*020L□□@5^++            | A    | 1                                   | 20               | 7.5          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.082          | 0.073          | 0.033          | 0.612          | 0.551          | 0.245          |
| TAZB105*020L□□@5^++            | B    | 1                                   | 20               | 4.8          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.121          | 0.109          | 0.048          | 0.580          | 0.522          | 0.232          |
| TAZB155*020L□□@5^++            | B    | 1.5                                 | 20               | 3.6          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.139          | 0.125          | 0.056          | 0.502          | 0.452          | 0.201          |
| TAZB225*020L□□@5^++            | B    | 2.2                                 | 20               | 3.6          | 0.110   | 1.100  | 1.320  | 6      | 8           | 8     | 0.070                             | 0.139          | 0.125          | 0.056          | 0.502          | 0.452          | 0.201          |
| TAZD225*020L□□@5^++            | D    | 2.2                                 | 20               | 1.7          | 0.225   | 2.250  | 2.700  | 6      | 8           | 8     | 0.080                             | 0.217          | 0.195          | 0.087          | 0.369          | 0.332          | 0.148          |
| TAZE335*020L□□@5^++            | E    | 3.3                                 | 20               | 1.2          | 0.165   | 1.650  | 1.980  | 6      | 8           | 8     | 0.090                             | 0.274          | 0.246          | 0.110          | 0.329          | 0.296          | 0.131          |
| TAZD475*020C□□@5^++            | D    | 4.7                                 | 20               | 6            | 0.235   | 2.350  | 2.820  | 6      | 8           | 8     | 0.080                             | 0.115          | 0.104          | 0.046          | 0.693          | 0.624          | 0.277          |
| TAZE475*020L□□@5^++            | E    | 4.7                                 | 20               | 1.7          | 0.235   | 2.350  | 2.820  | 6      | 8           | 8     | 0.090                             | 0.230          | 0.207          | 0.092          | 0.391          | 0.352          | 0.156          |
| TAZD685*020C□□@5^++            | D    | 6.8                                 | 20               | 4            | 0.450   | 4.500  | 5.400  | 6      | 8           | 8     | 0.080                             | 0.141          | 0.127          | 0.057          | 0.566          | 0.509          | 0.226          |
| TAZE685*020L□□@5^++            | E    | 6.8                                 | 20               | 1.5          | 0.450   | 4.500  | 5.400  | 6      | 8           | 8     | 0.090                             | 0.245          | 0.220          | 0.098          | 0.367          | 0.331          | 0.147          |
| TAZE106*020L□□@5^++            | E    | 10                                  | 20               | 1.5          | 0.500   | 5.000  | 6.000  | 6      | 8           | 8     | 0.090                             | 0.245          | 0.220          | 0.098          | 0.367          | 0.331          | 0.147          |
| TAZF156*020L□□@5^++            | F    | 15                                  | 20               | 0.8          | 0.750   | 7.500  | 9.000  | 6      | 8           | 8     | 0.100                             | 0.354          | 0.318          | 0.141          | 0.283          | 0.255          | 0.113          |
| TAZG156*020L□□@5^++            | G    | 15                                  | 20               | 0.275        | 0.750   | 7.500  | 9.000  | 6      | 8           | 8     | 0.125                             | 0.674          | 0.607          | 0.270          | 0.185          | 0.167          | 0.074          |
| TAZG226*020L□□@5^++            | G    | 22                                  | 20               | 0.625        | 1.100   | 11.000 | 13.200 | 6      | 8           | 8     | 0.125                             | 0.447          | 0.402          | 0.179          | 0.280          | 0.252          | 0.112          |
| TAZH226*020L□□@5^++            | H    | 22                                  | 20               | 0.18         | 1.100   | 11.000 | 13.200 | 6      | 8           | 8     | 0.150                             | 0.913          | 0.822          | 0.365          | 0.164          | 0.148          | 0.066          |
| TAZH476*020L□□@5^++            | H    | 47                                  | 20               | 0.18         | 2.350   | 23.500 | 28.200 | 8      | 10          | 10    | 0.150                             | 0.913          | 0.822          | 0.365          | 0.164          | 0.148          | 0.066          |
| TAZA334*025L□□@5^++            | A    | 0.33                                | 25               | 15           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.058          | 0.052          | 0.023          | 0.866          | 0.779          | 0.346          |
| TAZB105*025L□□@5^++            | B    | 1                                   | 25               | 4            | 0.160   | 1.600  | 1.920  | 6      | 8           | 8     | 0.070                             | 0.132          | 0.119          | 0.053          | 0.529          | 0.476          | 0.212          |
| TAZD155*025L□□@5^++            | D    | 1.5                                 | 25               | 1.7          | 0.200   | 2.000  | 2.400  | 6      | 8           | 8     | 0.080                             | 0.217          | 0.195          | 0.087          | 0.369          | 0.332          | 0.148          |
| TAZD225*025L□□@5^++            | D    | 2.2                                 | 25               | 2            | 0.215   | 2.150  | 2.580  | 6      | 8           | 8     | 0.080                             | 0.200          | 0.180          | 0.080          | 0.400          | 0.360          | 0.160          |
| TAZE225*025L□□@5^++            | E    | 2.2                                 | 25               | 1            | 0.230   | 2.300  | 2.760  | 6      | 8           | 8     | 0.090                             | 0.300          | 0.270          | 0.120          | 0.300          | 0.270          | 0.120          |
| TAZE335*025L□□@5^++            | E    | 3.3                                 | 25               | 1.2          | 0.245   | 2.450  | 2.940  | 6      | 8           | 8     | 0.090                             | 0.274          | 0.246          | 0.110          | 0.329          | 0.296          | 0.131          |
| TAZF475*025L□□@5^++            | F    | 4.7                                 | 25               | 0.7          | 0.294   | 2.938  | 3.525  | 6      | 8           | 8     | 0.100                             | 0.378          | 0.340          | 0.151          | 0.265          | 0.238          | 0.106          |
| TAZF685*025L□□@5^++            | F    | 6.8                                 | 25               | 0.8          | 0.425   | 4.250  | 5.100  | 6      | 8           | 8     | 0.100                             | 0.354          | 0.318          | 0.141          | 0.283          | 0.255          | 0.113          |
| TAZG106*025L□□@5^++            | G    | 10                                  | 25               | 0.35         | 0.625   | 6.250  | 7.500  | 6      | 8           | 8     | 0.125                             | 0.598          | 0.538          | 0.239          | 0.209          | 0.188          | 0.084          |
| TAZH226*025L□□@5^++            | H    | 22                                  | 25               | 0.18         | 1.375   | 13.750 | 16.500 | 6      | 8           | 8     | 0.150                             | 0.913          | 0.822          | 0.365          | 0.164          | 0.148          | 0.066          |
| TAZA224*035L□□@5^++            | A    | 0.22                                | 35               | 12           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.065          | 0.058          | 0.026          | 0.775          | 0.697          | 0.310          |
| TAZB474*035L□□@5^++            | B    | 0.47                                | 35               | 6.8          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.070                             | 0.101          | 0.091          | 0.041          | 0.690          | 0.621          | 0.276          |
| TAZD105*035L□□@5^++            | D    | 1                                   | 35               | 2.2          | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.080                             | 0.191          | 0.172          | 0.076          | 0.420          | 0.378          | 0.168          |
| TAZF335*035L□□@5^++            | F    | 3.3                                 | 35               | 0.7          | 0.289   | 2.888  | 3.465  | 6      | 8           | 8     | 0.100                             | 0.378          | 0.340          | 0.151          | 0.265          | 0.238          | 0.106          |
| TAZH106*035L□□@5^++            | H    | 10                                  | 35               | 0.5          | 0.875   | 8.750  | 10.500 | 8      | 10          | 10    | 0.150                             | 0.548          | 0.493          | 0.219          | 0.274          | 0.246          | 0.110          |
| TAZA104*050L□□@5^++            | A    | 0.1                                 | 50               | 12           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.065          | 0.058          | 0.026          | 0.775          | 0.697          | 0.310          |
| TAZA154*050L□□@5^++            | A    | 0.15                                | 50               | 12           | 0.100   | 1.000  | 1.200  | 6      | 8           | 8     | 0.050                             | 0.065          | 0.058          | 0.026          | 0.775          | 0.697          | 0.310          |
| TAZE105*050L□□@5^++            | E    | 1                                   | 50               | 1.7          | 0.125   | 1.250  | 1.500  | 6      | 8           | 8     | 0.090                             | 0.230          | 0.207          | 0.092          | 0.391          | 0.352          | 0.156          |
| TAZF225*050L□□@5^++            | F    | 2.2                                 | 50               | 0.7          | 0.275   | 2.750  | 3.300  | 6      | 8           | 8     | 0.100                             | 0.378          | 0.340          | 0.151          | 0.265          | 0.238          | 0.106          |
| TAZG335*050L□□@5^++            | G    | 3.3                                 | 50               | 0.5          | 0.413   | 4.125  | 4.950  | 6      | 8           | 8     | 0.125                             | 0.500          | 0.450          | 0.200          | 0.250          | 0.225          | 0.100          |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

# TAZ Series



## HRC6000 Medical Implantable Grade



The TAZ HRC6000 Medical Grade series is the next generation of our internally qualified implantable medical grade tantalum capacitors. These components are screened using our newly designed Q-Process to effectively remove components that may experience parametric shifts through customer processing or display instability through life testing.


Due to the deficiencies of Weibull grading and its tendency to Burn-In potentially unstable units, this Q-Process utilizes a Product Level Designation system based on a simulated production routine performed on a sample from the population. Once that is completed a

calculation is done based on the performance of the sample which can take into account the application conditions of the end customer. This system also allows for derating recommendations to be relaxed as illustrated by the section below.

These components are manufactured and tested in the AVX Biddeford Maine facility which is ISO 13485 certified. For more information on this process or to request a specific rating please contact the factory. In addition, DC leakage testing at application voltage is available upon request.

### CASE DIMENSIONS:

millimeters (inches)



| Case Code | Length (L)<br>±0.38<br>(0.015) | Width (W)<br>±0.38<br>(0.015) | Height (H)<br>±0.38<br>(0.015) | Term. Width (W <sub>t</sub> )           | Term. Length (A)<br>+0.25/-0.13<br>(+0.010/-0.005) | S min           | Typical Weight (g) |
|-----------|--------------------------------|-------------------------------|--------------------------------|---|--|-----------------|--------------------|
| E         | 5.08<br>(0.200)                | 2.54<br>(0.100)               | 1.27<br>(0.050)                | 2.41+0.13/-0.25<br>(0.095+0.005/-0.010) | 0.76<br>(0.030)                                    | 2.92<br>(0.115) | 0.065              |
| H         | 7.24<br>(0.285)                | 3.81<br>(0.150)               | 2.79<br>(0.110)                | 3.68+0.13/-0.51<br>(0.145+0.005/-0.020) | 1.27<br>(0.050)                                    | 4.06<br>(0.160) | 0.035              |

### MARKING

(White marking on black body)



Polarity Stripe (+)

Capacitance Code  
Rated Voltage

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage |    |     |     |
|-------------|------|---------------|----|-----|-----|
| μF          | Code | 4V            | 6V | 10V | 15V |
| 10          | 106  |               |    |     | E   |
| 15          | 156  |               |    | E   |     |
| 22          | 226  |               | E  |     |     |
| 33          | 336  | E             |    |     |     |
| 47          | 476  |               |    |     |     |
| 68          | 686  |               |    |     |     |
| 100         | 107  |               |    | H   |     |
| 150         | 157  |               | H  |     |     |
| 220         | 227  |               | H  |     |     |
| 330         | 337  | H             |    |     |     |

Available ratings


# TAZ Series




## HRC6000 Medical Implantable Grade

### HOW TO ORDER

| TAZ         | E                | 106   | *   | 015   | C  | □  | L                                      | Q   | 6   | ^   | ++  |
|-------------|------------------|---|---|---|--|--|--|---|---|---|---|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>J = ±5%<br>K = ±10%<br>M = ±20% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc | <b>ESR</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>W = Waffle | <b>Inspection Level</b><br>L = Group A | <b>Reliability Grade</b><br>Product Level Designator:<br>Q = 0.1%/1000 hrs. Minimum, 60% conf | <b>Qualification Level</b><br>6 = HRC6000 | <b>Termination Finish</b><br>H = Solder Plated<br>0 = Solder Fused<br>9 = Gold Plated<br>7 = 100% Tin | <b>Surge Test Option</b><br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 Cycles, -55°C & +85°C before Weibull |



LEAD-FREE  
LEAD-FREE COMPATIBLE COMPONENT



RoHS  
COMPLIANT

For RoHS compliant products, please select correct termination style.

\*Contact factory for AVX HRC6000 Medical Grade SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |   |     |    |
|------------------------------------|---|-----|---|-----|----|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |   |     |    |
| Capacitance Range:                 | 10 µF to 330 µF   |     |   |     |    |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |   |     |    |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6 | 10  | 15 |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4 | 6.7 | 10 |
| Temperature Range:                 | -55°C to +125°C   |     |   |     |    |

# TAZ Series



## HRC6000 Medical Implantable Grade

| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating |                  |              |         |       |        |        |             |       | Typical RMS Ripple Data by Rating |                     |                     |                      |                     |                     |                      |
|--------------------------------|------|-------------------------------------|------------------|--------------|---------|-------|--------|--------|-------------|-------|-----------------------------------|---------------------|---------------------|----------------------|---------------------|---------------------|----------------------|
|                                |      | Cap @ 120Hz                         | DC Rated Voltage | ESR @ 100kHz | DCL max |       |        | DF max |             |       | Power Dissipation                 | 25°C Ripple Current | 85°C Ripple Current | 125°C Ripple Current | 25°C Ripple Voltage | 85°C Ripple Voltage | 125°C Ripple Voltage |
|                                |      |                                     |                  |              | +25°C   | +85°C | +125°C | +25°C  | +(85/125)°C | -55°C |                                   |                     |                     |                      |                     |                     |                      |
| AVX HRC6000 P/N                | Case | µF @ 25°C                           | V @ +85°C        | Ohms @ +25°C | (µA)    | (µA)  | (µA)   | (%)    | (%)         | (%)   |                                   |                     |                     |                      |                     |                     |                      |
| TAZE336*004C□L@6^++            | E    | 33                                  | 4                | 3            | 0.33    | 3.3   | 3.96   | 8      | 10          | 12    | 0.090                             | 0.173               | 0.156               | 0.069                | 0.519               | 0.468               | 0.207                |
| TAZH337*004C□L@6^++            | H    | 330                                 | 4                | 0.9          | 3.30    | 33.0  | 39.6   | 10     | 12          | 12    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZE226*006C□L@6^++            | E    | 22                                  | 6                | 3.5          | 0.33    | 3.3   | 3.96   | 8      | 10          | 12    | 0.090                             | 0.160               | 0.144               | 0.064                | 0.561               | 0.505               | 0.224                |
| TAZH157*006C□L@6^++            | H    | 150                                 | 6                | 0.9          | 2.25    | 22.5  | 27.0   | 10     | 12          | 12    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZH227*006C□L@6^++            | H    | 220                                 | 6                | 0.9          | 3.30    | 33.0  | 39.6   | 10     | 12          | 12    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZE156*010C□LQ6^++            | E    | 15                                  | 10               | 3            | 0.375   | 3.75  | 4.50   | 8      | 10          | 10    | 0.090                             | 0.173               | 0.156               | 0.069                | 0.520               | 0.468               | 0.208                |
| TAZH107*010C□L@6^++            | H    | 100                                 | 10               | 0.9          | 2.50    | 25.0  | 30.0   | 10     | 12          | 12    | 0.090                             | 0.316               | 0.285               | 0.126                | 0.285               | 0.256               | 0.114                |
| TAZE106*015C□LQ6^++            | E    | 10                                  | 15               | 4            | 0.375   | 3.75  | 4.50   | 6      | 8           | 8     | 0.090                             | 0.150               | 0.135               | 0.060                | 0.600               | 0.540               | 0.240                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

## HRC6000 DERATING GUIDELINES

Due to our new Q-Process technology the need for a typical 50% derating of the capacitors rated voltage in application can be relaxed. Below is a table outlining some of the common applications where these components are utilized along with appropriate derating recommendations. When determining the appropriate capacitor voltage rating to utilize, the application voltage is determined by the maximum D.C. voltage with the addition of any A.C. ripple voltage that may be present.

| Recommended Derating | Application |
|----------------------|-------------|
| 20%                  | Filtering   |
| 0%                   | Pacing      |
| 0%                   | Hold-Up     |
| 0%                   | Charging    |

# TCP Series - DSCC 09009



## TCP Series Low ESR Tantalum Modules



TCP Series tantalum modules represent high packing density for applications utilizing multiple components in a parallel configuration, and are available with testing to DSCC 09009.

These modules feature stacked assemblies of CWR29 capacitors which provide ultra low ESR and utilize established reliability capacitors (Weibull Grade voltage conditioning) in accordance with MIL-PRF-55365. They can also be supplied with SRC9000 Space Level components.

The stacked construction of fully molded capacitors is compatible with a wide range of SMT board assembly processes including reflow solder or conductive epoxy.


There are two termination finishes available: hot solder dipped ("C") and gold plated ("B").

The molding compound has been selected to meet the requirements of UL94V-0 and out-gassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.

**Note: Additional form factors and ratings are available.  
Contact plant for details.**

### DIMENSIONS



### CASE DIMENSIONS:

millimeters (inches)

| Case Code | Length (L)<br>±0.38 (0.015) | Width (W)<br>±0.38 (0.015) | Height (H)<br>±0.38 (0.015) | Term. Width (W <sub>t</sub> )<br>±0.38 (0.015) | Term. Length (P)<br>For Reference Only |
|-----------|-----------------------------|----------------------------|-----------------------------|--|--|
| 2H        | 7.82 (0.308)                | 4.06 (0.160)               | 6.10 (0.240)                | 4.06 (0.160)                                   | 1.52 (0.060)                           |
| 4H        | 7.82 (0.308)                | 8.13 (0.320)               | 6.10 (0.240)                | 8.13 (0.320)                                   | 1.52 (0.060)                           |
| 6H        | 7.82 (0.308)                | 8.13 (0.320)               | 9.14 (0.360)                | 8.13 (0.320)                                   | 1.52 (0.060)                           |

Additional form factors and ratings are available – contact plant for details.

### CAPACITANCE AND RATED VOLTAGE CASE SIZE (ESR IN mΩ)

| Capacitance |      | Rated voltage DC (V <sub>R</sub> ) to 85°C |         |         |         |         |          |          |
|-------------|------|--|---------|---------|---------|---------|----------|----------|
| μF          | Code | 6V   | 10V     | 15V     | 20V     | 25V     | 35V      | 50V      |
| 9.4         | 945  |  |         |         |         |         |          | 2H (200) |
| 18.8        | 196  |  |         |         |         |         |          | 4H (100) |
| 20          | 206  |  |         |         |         |         | 2H (200) |          |
| 28.2        | 286  |  |         |         |         |         |          | 6H (67)  |
| 40          | 406  |  |         |         |         |         | 4H (100) |          |
| 60          | 606  |  |         |         |         |         | 6H (67)  |          |
| 66          | 666  |  |         |         |         | 2H (85) |          |          |
| 94          | 946  |  |         |         | 2H (75) |         |          |          |
| 132         | 137  |  |         |         |         | 4H (43) |          |          |
| 188         | 197  |  |         |         | 4H (38) |         |          |          |
| 198         | 207  |  |         |         |         | 6H (28) |          |          |
| 200         | 207  |  |         | 2H (63) |         |         |          |          |
| 282         | 287  |  |         |         | 6H (25) |         |          |          |
| 400         | 407  |  |         | 4H (31) |         |         |          |          |
| 440         | 447  |  | 2H (50) |         |         |         |          |          |
| 600         | 607  |  |         | 6H (21) |         |         |          |          |
| 660         | 667  | 2H (50)                                    |         |         |         |         |          |          |
| 880         | 887  |  | 4H (25) |         |         |         |          |          |
| 1,320       | 138  | 4H (25)                                    | 6H (17) |         |         |         |          |          |
| 1,980       | 208  | 6H (17)                                    |         |         |         |         |          |          |



# TCP Series - DSCC 09009



## TCP Series Low ESR Tantalum Modules

### HOW TO ORDER

| TC          | 2H               | 945   | K   | 050   | L   | R  | #  | @   | 0  | ^   | ++  |
|-------------|------------------|---|---|---|---|--|--|---|--|---|---|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Standard or Low ESR Range</b><br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R | <b>Inspection Level</b><br>S = Std. Conformance<br>L = Group A<br>D = DSCC DWG | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>Z = Non-ER | <b>Qualification Level</b><br>0 = N/A<br>9 = SRC9000 | <b>Termination Finish</b><br>8 = Hot Solder Dipped<br>9 = Gold Plated | <b>Surge Test Option</b><br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |



### DSCC DWG P/N:

| 09009                    | -01                                     | K  | B   | C  | A   |
|--------------------------|---|--|---|--|---|
| <b>DSCC DWG</b><br>09009 | <b>Dash Number</b><br>See Rating Tables | <b>Capacitance Tolerance</b><br>K = ±10%<br>M = ±20% | <b>Reliability Grade</b><br>B = B Weibull<br>C = C Weibull<br>D = D Weibull | <b>Termination Finish</b><br>B = Gold Plated (10 microinch minimum)<br>C = Hot Solder Dip (60 microinch minimum) | <b>Surge Test Option</b><br>A = 10 cycles, +25°C<br>B = 10 cycles, -55°C & +85°C<br>C = 10 cycles, -55°C & +85°C before Weibull<br>Z = None required<br>Per MIL-PRF-55365 |



### TECHNICAL SPECIFICATIONS

|                                    |   |     |      |      |      |      |      |      |  |  |
|------------------------------------|---|-----|------|------|------|------|------|------|--|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |      |      |      |      |      |      |  |  |
| Capacitance Range:                 | 9.4 µF to 1,980 µF  |     |      |      |      |      |      |      |  |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |      |      |      |      |      |      |  |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 6   | 10   | 15   | 20   | 25   | 35   | 50   |  |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 4   | 6.7  | 10   | 13.3 | 16.7 | 23.3 | 33.3 |  |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 8   | 13.3 | 20   | 26.7 | 33.3 | 46.7 | 66.7 |  |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 5.3 | 8.7  | 13.3 | 17.8 | 22.2 | 31.1 | 44.5 |  |  |
| Temperature Range:                 | -55°C to +125°C   |     |      |      |      |      |      |      |  |  |

# TCP Series



## TCP Series Low ESR Tantalum Modules

### RATINGS & PART NUMBER REFERENCE

| 2-STACK             |               |      | Parametric Specifications by Rating |           |                              |                     |       |        |                            |             |       | Typical RMS Ripple Data by Rating |       |        |                              |       |        |
|---------------------|---------------|------|-------------------------------------|-----------|------------------------------|---------------------|-------|--------|----------------------------|-------------|-------|-----------------------------------|-------|--------|------------------------------|-------|--------|
| AVX P/N             | DSCC P/N      | Case | Cap<br>µF                           | Volt<br>V | ESR<br>@ 100 kHz<br>+25°C mΩ | DC Leakage (max) µA |       |        | Dissipation Factor (max) % |             |       | 100kHz Ripple Current Rating      |       |        | 100kHz Ripple Voltage Rating |       |        |
|                     |               |      |                                     |           |                              | +25°C               | +85°C | +125°C | +25°C                      | +(85/125)°C | -55°C | A                                 | A     | A      | V                            | V     | V      |
|                     |               |      |                                     |           |                              | +25°C               | +85°C | +125°C | +25°C                      | +(85/125)°C | -55°C | +25°C                             | +85°C | +125°C | +25°C                        | +85°C | +125°C |
| TC2H667*006L□#@00++ | 09009-001*^+^ | 2H   | 660                                 | 6         | 50                           | 39.6                | 396   | 495    | 10                         | 12          | 12    | 2.45                              | 2.20  | 0.98   | 0.12                         | 0.11  | 0.05   |
| TC2H447*010L□#@00++ | 09009-002*^+^ | 2H   | 440                                 | 10        | 50                           | 44                  | 440   | 550    | 10                         | 12          | 12    | 2.45                              | 2.20  | 0.98   | 0.12                         | 0.11  | 0.05   |
| TC2H207*015L□#@00++ | 09009-003*^+^ | 2H   | 200                                 | 15        | 63                           | 30                  | 300   | 375    | 10                         | 12          | 12    | 2.19                              | 1.97  | 0.88   | 0.14                         | 0.12  | 0.05   |
| TC2H946*020L□#@00++ | 09009-004*^+^ | 2H   | 94                                  | 20        | 75                           | 18.8                | 188   | 235    | 8                          | 10          | 10    | 2.00                              | 1.80  | 0.80   | 0.15                         | 0.14  | 0.06   |
| TC2H666*025L□#@00++ | 09009-005*^+^ | 2H   | 66                                  | 25        | 85                           | 16.5                | 165   | 206    | 8                          | 10          | 10    | 1.88                              | 1.69  | 0.75   | 0.16                         | 0.14  | 0.06   |
| TC2H206*035L□#@00++ | 09009-006*^+^ | 2H   | 20                                  | 35        | 200                          | 7                   | 70    | 88     | 8                          | 10          | 10    | 1.22                              | 1.10  | 0.49   | 0.24                         | 0.22  | 0.10   |
| TC2H945*050L□#@00++ | 09009-007*^+^ | 2H   | 9.4                                 | 50        | 200                          | 4.7                 | 47    | 59     | 6                          | 8           | 8     | 1.22                              | 1.10  | 0.49   | 0.24                         | 0.22  | 0.10   |

| 4-STACK             |               |      | Parametric Specifications by Rating |           |                              |                     |       |        |                            |             |       | Typical RMS Ripple Data by Rating |       |        |                              |       |        |
|---------------------|---------------|------|-------------------------------------|-----------|------------------------------|---------------------|-------|--------|----------------------------|-------------|-------|-----------------------------------|-------|--------|------------------------------|-------|--------|
| AVX P/N             | DSCC P/N      | Case | Cap<br>µF                           | Volt<br>V | ESR<br>@ 100 kHz<br>+25°C mΩ | DC Leakage (max) µA |       |        | Dissipation Factor (max) % |             |       | 100kHz Ripple Current Rating      |       |        | 100kHz Ripple Voltage Rating |       |        |
|                     |               |      |                                     |           |                              | +25°C               | +85°C | +125°C | +25°C                      | +(85/125)°C | -55°C | A                                 | A     | A      | V                            | V     | V      |
|                     |               |      |                                     |           |                              | +25°C               | +85°C | +125°C | +25°C                      | +(85/125)°C | -55°C | +25°C                             | +85°C | +125°C | +25°C                        | +85°C | +125°C |
| TC4H138*006L□#@00++ | 09009-008*^+^ | 4H   | 1320                                | 6         | 25                           | 79.2                | 792   | 990    | 10                         | 12          | 12    | 4.90                              | 4.41  | 1.96   | 0.12                         | 0.11  | 0.05   |
| TC4H887*010L□#@00++ | 09009-009*^+^ | 4H   | 880                                 | 10        | 25                           | 88                  | 880   | 1100   | 10                         | 12          | 12    | 4.90                              | 4.41  | 1.96   | 0.12                         | 0.11  | 0.05   |
| TC4H407*015L□#@00++ | 09009-010*^+^ | 4H   | 400                                 | 15        | 31                           | 60                  | 600   | 750    | 10                         | 12          | 12    | 4.38                              | 3.94  | 1.75   | 0.14                         | 0.12  | 0.05   |
| TC4H197*020L□#@00++ | 09009-011*^+^ | 4H   | 188                                 | 20        | 38                           | 37.6                | 376   | 470    | 8                          | 10          | 10    | 4.00                              | 3.60  | 1.60   | 0.15                         | 0.14  | 0.06   |
| TC4H137*025L□#@00++ | 09009-012*^+^ | 4H   | 132                                 | 25        | 43                           | 33                  | 330   | 413    | 8                          | 10          | 10    | 3.74                              | 3.36  | 1.49   | 0.16                         | 0.14  | 0.06   |
| TC4H406*035L□#@00++ | 09009-013*^+^ | 4H   | 40                                  | 35        | 100                          | 14                  | 140   | 175    | 8                          | 10          | 10    | 2.45                              | 2.20  | 0.98   | 0.24                         | 0.22  | 0.10   |
| TC4H196*050L□#@00++ | 09009-014*^+^ | 4H   | 18.8                                | 50        | 100                          | 9.4                 | 94    | 118    | 6                          | 8           | 8     | 2.45                              | 2.20  | 0.98   | 0.24                         | 0.22  | 0.10   |

| 6-STACK             |               |      | Parametric Specifications by Rating |           |                              |                     |       |        |                            |             |       | Typical RMS Ripple Data by Rating |       |        |                              |       |        |
|---------------------|---------------|------|-------------------------------------|-----------|------------------------------|---------------------|-------|--------|----------------------------|-------------|-------|-----------------------------------|-------|--------|------------------------------|-------|--------|
| AVX P/N             | DSCC P/N      | Case | Cap<br>µF                           | Volt<br>V | ESR<br>@ 100 kHz<br>+25°C mΩ | DC Leakage (max) µA |       |        | Dissipation Factor (max) % |             |       | 100kHz Ripple Current Rating      |       |        | 100kHz Ripple Voltage Rating |       |        |
|                     |               |      |                                     |           |                              | +25°C               | +85°C | +125°C | +25°C                      | +(85/125)°C | -55°C | A                                 | A     | A      | V                            | V     | V      |
|                     |               |      |                                     |           |                              | +25°C               | +85°C | +125°C | +25°C                      | +(85/125)°C | -55°C | +25°C                             | +85°C | +125°C | +25°C                        | +85°C | +125°C |
| TC6H208*006L□#@00++ | 09009-015*^+^ | 6H   | 1980                                | 6         | 17                           | 118.8               | 1188  | 1485   | 10                         | 12          | 12    | 7.35                              | 6.61  | 2.94   | 0.12                         | 0.11  | 0.05   |
| TC6H138*010L□#@00++ | 09009-016*^+^ | 6H   | 1320                                | 10        | 17                           | 132                 | 1320  | 1650   | 10                         | 12          | 12    | 7.35                              | 6.61  | 2.94   | 0.12                         | 0.11  | 0.05   |
| TC6H607*015L□#@00++ | 09009-017*^+^ | 6H   | 600                                 | 15        | 21                           | 90                  | 900   | 1125   | 10                         | 12          | 12    | 6.57                              | 5.92  | 2.63   | 0.14                         | 0.12  | 0.05   |
| TC6H287*020L□#@00++ | 09009-018*^+^ | 6H   | 282                                 | 20        | 25                           | 56.4                | 564   | 705    | 8                          | 10          | 10    | 6.00                              | 5.40  | 2.40   | 0.15                         | 0.14  | 0.06   |
| TC6H207*025L□#@00++ | 09009-019*^+^ | 6H   | 198                                 | 25        | 28                           | 49.5                | 495   | 619    | 8                          | 10          | 10    | 5.67                              | 5.10  | 2.27   | 0.16                         | 0.14  | 0.06   |
| TC6H606*035L□#@00++ | 09009-020*^+^ | 6H   | 60                                  | 35        | 67                           | 21                  | 210   | 263    | 8                          | 10          | 10    | 3.67                              | 3.31  | 1.47   | 0.24                         | 0.22  | 0.10   |
| TC6H286*050L□#@00++ | 09009-021*^+^ | 6H   | 28.2                                | 50        | 67                           | 14.1                | 141   | 176    | 6                          | 8           | 8     | 3.67                              | 3.31  | 1.47   | 0.24                         | 0.22  | 0.10   |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# TBJ Series



## CWR11 - MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level



Fully qualified to MIL-PRF-55365/8, the CWR11 is the military version of EIA-535BAAC, with four case sizes designed for maximum packaging efficiency on 8mm & 12mm tape for high volume production (ensuring no TCE mismatch with any substrate). This construction is compatible with a wide range of SMT board assembly processes including wave or reflow solder, conductive epoxy or compression bonding techniques. The part also carries full polarity, capacitance / voltage and JAN brand marking.


For Space Level applications, AVX SRC9000 qualification is recommended (see ratings table for part number availability).

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these are "H", "K", "C" and "B" termination, respectively, per MIL-PRF-55365).

The molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.

The series is qualified to MIL-PRF-55365 Weibull "B", "C", "D" and "T" levels, with all surge options ("A", "B" & "C") available.



### MARKING

(Brown marking on gold body)



Polarity Stripe (+)

"J" for "JAN" Brand  
Capacitance Code

Rated Voltage  
Manufacturer's ID

### CASE DIMENSIONS: millimeters (inches)

| Case Code | EIA Metric | Length (L)                 | Width (W)                  | Height (H)                 | Term. Width (W <sub>1</sub> )<br>±0.10 (±0.004) | Term. Length A<br>±0.30(±0.012) | S min        |
|-----------|------------|----------------------------|----------------------------|----------------------------|---|---------------------------------|--------------|
| A         | 3216-18    | 3.20±0.20<br>(0.126±0.008) | 1.60±0.20<br>(0.063±0.008) | 1.60±0.20<br>(0.063±0.008) | 1.20 (0.047)                                    | 0.80 (0.031)                    | 1.80 (0.071) |
| B         | 3528-21    | 3.50±0.20<br>(0.138±0.008) | 2.80±0.20<br>(0.110±0.008) | 1.90±0.20<br>(0.075±0.008) | 2.20 (0.087)                                    | 0.80 (0.031)                    | 1.40 (0.055) |
| C         | 6032-28    | 6.00±0.30<br>(0.236±0.012) | 3.20±0.30<br>(0.126±0.012) | 2.50±0.30<br>(0.098±0.012) | 2.20 (0.087)                                    | 1.30 (0.051)                    | 2.90 (0.114) |
| D         | 7343-31    | 7.30±0.30<br>(0.287±0.012) | 4.30±0.30<br>(0.169±0.012) | 2.80±0.30<br>(0.110±0.012) | 2.40 (0.094)                                    | 1.30 (0.051)                    | 4.40 (0.173) |

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (MIL VOLTAGE CODE) RANGE CASE SIZE

| Capacitance |      | Rated voltage DC (V <sub>R</sub> ) to 85°C |        |         |         |         |         |         |         |
|-------------|------|--|--------|---------|---------|---------|---------|---------|---------|
| μF          | Code | 4V (C)                                     | 6V (D) | 10V (F) | 15V (H) | 20V (J) | 25V (K) | 35V (M) | 50V (N) |
| 0.10        | 104  |  |        |         |         |         |         | A       | A       |
| 0.15        | 154  |  |        |         |         |         |         | A       | B       |
| 0.22        | 224  |  |        |         |         |         |         | A       | B       |
| 0.33        | 334  |  |        |         |         |         | A       | A       | B       |
| 0.47        | 474  |  |        |         | A       | A       | A       | B       | C       |
| 0.68        | 684  |  |        |         | A       | A       | B       | B       | C       |
| 1.0         | 105  |  |        | A       | A       | A       | B       | B       | C       |
| 1.5         | 155  |  | A      | A       | A       | B       | B       | C       | D       |
| 2.2         | 225  | A  | A      | A       | B       | B       | C       | C       | D       |
| 3.3         | 335  |  | A      | B       | B       | B       | C       | C       | D       |
| 4.7         | 475  | A  | B      | B       | B       | C       | C       | D       | D       |
| 6.8         | 685  | B  | B      | B       |         | C       | D       | D       |         |
| 10          | 106  | B  | B      |         | C       |         | D       |         |         |
| 15          | 156  | B  | C      | C       |         | D       | D       |         |         |
| 22          | 226  |  | C      |         | D       | D       |         |         |         |
| 33          | 336  | C  |        | D       | D       |         |         |         |         |
| 47          | 476  |  | D      | D       |         |         |         |         |         |
| 68          | 686  | D  | D      |         |         |         |         |         |         |
| 100         | 107  | D  |        |         |         |         |         |         |         |

# TBJ Series



## CWR11 - MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level

### HOW TO ORDER

#### COTS-PLUS & MIL QPL (CWR11):

|             |                  |   |   |   |  |   |   |   |   |  |   |
|-------------|------------------|---|---|---|--|---|---|---|---|--|---|
| <b>TBJ</b>  | <b>D</b>         | <b>686</b>  | <b>*</b>  | <b>006</b>  | <b>C</b>   | <b>□</b>  | <b>#</b>  | <b>@</b>  | <b>0</b>  | <b>^</b>   | <b>++</b>   |
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>S = Std. Conformance<br>L = Group A<br><br>M = MIL (JAN) CWR11 | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>Z = Non-ER | <b>Qualification Level</b><br>0 = N/A<br>T = T Level<br><br>9 = SRC9000 | <b>Termination Finish</b><br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated<br>7 = Matte Sn (COTS-Plus only) | <b>Surge Test Option</b><br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

#### CWR11 P/N CROSS REFERENCE:

|              |   |  |   |   |  |  |  |
|--------------|---|--|---|---|--|--|--|
| <b>CWR11</b> | <b>D</b>  | <b>^</b>   | <b>686</b>  | <b>*</b>  | <b>@</b>   | <b>+</b>   | <b>□</b>   |
| <b>Type</b>  | <b>Voltage Code</b><br>C = 4Vdc<br>D = 6Vdc<br>F = 10Vdc<br>H = 15Vdc<br>J = 20Vdc<br>K = 25Vdc<br>M = 35Vdc<br>N = 50Vdc | <b>Termination Finish</b><br>H = Solder Plated<br>K = Solder Fused<br>C = Hot Solder Dipped<br>B = Gold Plated | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>T = T Level<br>A = Non-ER | <b>Surge Test Option</b><br>A = 10 cycles, +25°C<br>B = 10 cycles, -55°C & +85°C<br>C = 10 cycles, -55°C & +85°C before Weibull<br><br>If blank, None required | <b>Packaging</b><br>Bulk = Standard<br>TR = 7" T&R<br>TR13 = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. |

For RoHS compliant products, please select correct termination style.

#### SPACE LEVEL OPTIONS TO SRC9000\*:

|             |                  |   |   |   |  |   |  |   |   |   |  |
|-------------|------------------|---|---|---|--|---|--|---|---|---|--|
| <b>TBJ</b>  | <b>D</b>         | <b>686</b>  | <b>*</b>  | <b>006</b>  | <b>C</b>   | <b>□</b>  | <b>L</b>                               | <b>@</b>  | <b>9</b>                                  | <b>^</b>  | <b>++</b>  |
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>015 = 15Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>L = Group A | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf. | <b>Qualification Level</b><br>9 = SRC9000 | <b>Termination Finish</b><br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated | <b>Surge Test Option</b><br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |     |      |      |      |      |      |      |  |
|------------------------------------|---|-----|-----|------|------|------|------|------|------|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |     |      |      |      |      |      |      |  |
| Capacitance Range:                 | 0.10 µF to 100 µF   |     |     |      |      |      |      |      |      |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |     |      |      |      |      |      |      |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6   | 10   | 16   | 20   | 25   | 35   | 50   |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4   | 6.7  | 10   | 13.3 | 16.7 | 23.3 | 33.3 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 5.3 | 8   | 13.3 | 20   | 26.7 | 33.3 | 46.7 | 66.7 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 3.5 | 5.3 | 8.7  | 13.3 | 17.8 | 22.2 | 31.1 | 44.5 |  |
| Temperature Range:                 | -55°C to +125°C   |     |     |      |      |      |      |      |      |  |



## CWR11 - MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                               |                               | Parametric Specifications by Rating per MIL-PRF-55365/8 |                                     |                                    |         |       |       |        |       |       | Typical RMS Ripple Data by Rating |                                 |                                 |                                  |                                 |                                 |                                  |      |
|--------------------------------|-------------------------------|-------------------------------|---|-------------------------------------|------------------------------------|---------|-------|-------|--------|-------|-------|-----------------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|------|
|                                |                               |                               | Cap<br>@ 120Hz<br>µF<br>@ 25°C                          | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |       |       | DF Max |       |       | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |      |
| CWR11 P/N                      | AVX COTS-Plus P/N             | AVX SRC9000 P/N               | Case  | +25°C                               | +85°C                              | +125°C  | +25°C | +85°C | +125°C | +25°C | +85°C | +125°C                            | W                               | A                               | A                                | A                               | V                               | V                                | V    |
| CWR11C^225^@+□                 | TBJA 225 * 004 C □ # @ 0 ^ ++ | TBJA 225 * 004 C □ L @ 9 ^ ++ | A   | 2.2                                 | 4                                  | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11C^475^@+□                 | TBJA 475 * 004 C □ # @ 0 ^ ++ | TBJA 475 * 004 C □ L @ 9 ^ ++ | A   | 4.7                                 | 4                                  | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11C^685^@+□                 | TBJB 685 * 004 C □ # @ 0 ^ ++ | TBJB 685 * 004 C □ L @ 9 ^ ++ | B   | 6.8                                 | 4                                  | 5.5     | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.12                            | 0.11                             | 0.05                            | 0.68                            | 0.62                             | 0.27 |
| CWR11C^106^@+□                 | TBJB 106 * 004 C □ # @ 0 ^ ++ | TBJB 106 * 004 C □ L @ 9 ^ ++ | B   | 10                                  | 4                                  | 4       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.15                            | 0.13                             | 0.06                            | 0.58                            | 0.52                             | 0.23 |
| CWR11C^156^@+□                 | TBJB 156 * 004 C □ # @ 0 ^ ++ | TBJB 156 * 004 C □ L @ 9 ^ ++ | B   | 15                                  | 4                                  | 3.5     | 0.6   | 6     | 7.2    | 6     | 9     | 9                                 | 0.085                           | 0.16                            | 0.14                             | 0.06                            | 0.55                            | 0.49                             | 0.22 |
| CWR11C^336^@+□                 | TBJC 336 * 004 C □ # @ 0 ^ ++ | TBJC 336 * 004 C □ L @ 9 ^ ++ | C   | 33                                  | 4                                  | 2.2     | 1.3   | 13    | 15.6   | 6     | 9     | 9                                 | 0.110                           | 0.22                            | 0.20                             | 0.09                            | 0.49                            | 0.44                             | 0.20 |
| CWR11C^686^@+□                 | TBJD 686 * 004 C □ # @ 0 ^ ++ | TBJD 686 * 004 C □ L @ 9 ^ ++ | D   | 68                                  | 4                                  | 1.1     | 2.7   | 27    | 32.4   | 6     | 9     | 9                                 | 0.150                           | 0.37                            | 0.33                             | 0.15                            | 0.41                            | 0.37                             | 0.16 |
| CWR11C^107^@+□                 | TBJD 107 * 004 C □ # @ 0 ^ ++ | TBJD 107 * 004 C □ L @ 9 ^ ++ | D   | 100                                 | 4                                  | 0.9     | 4     | 40    | 48     | 8     | 12    | 12                                | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR11D^155^@+□                 | TBJA 155 * 006 C □ # @ 0 ^ ++ | TBJA 155 * 006 C □ L @ 9 ^ ++ | A   | 1.5                                 | 6                                  | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11D^225^@+□                 | TBJA 225 * 006 C □ # @ 0 ^ ++ | TBJA 225 * 006 C □ L @ 9 ^ ++ | A   | 2.2                                 | 6                                  | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11D^335^@+□                 | TBJA 335 * 006 C □ # @ 0 ^ ++ | TBJA 335 * 006 C □ L @ 9 ^ ++ | A   | 3.3                                 | 6                                  | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11D^475^@+□                 | TBJB 475 * 006 C □ # @ 0 ^ ++ | TBJB 475 * 006 C □ L @ 9 ^ ++ | B   | 4.7                                 | 6                                  | 5.5     | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.12                            | 0.11                             | 0.05                            | 0.68                            | 0.62                             | 0.27 |
| CWR11D^685^@+□                 | TBJB 685 * 006 C □ # @ 0 ^ ++ | TBJB 685 * 006 C □ L @ 9 ^ ++ | B   | 6.8                                 | 6                                  | 4.5     | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.14                            | 0.12                             | 0.05                            | 0.62                            | 0.56                             | 0.25 |
| CWR11D^106^@+□                 | TBJB 106 * 006 C □ # @ 0 ^ ++ | TBJB 106 * 006 C □ L @ 9 ^ ++ | B   | 10                                  | 6                                  | 3.5     | 0.6   | 6     | 7.2    | 6     | 9     | 9                                 | 0.085                           | 0.16                            | 0.14                             | 0.06                            | 0.55                            | 0.49                             | 0.22 |
| CWR11D^156^@+□                 | TBJC 156 * 006 C □ # @ 0 ^ ++ | TBJC 156 * 006 C □ L @ 9 ^ ++ | C   | 15                                  | 6                                  | 3       | 0.9   | 9     | 10.8   | 6     | 9     | 9                                 | 0.110                           | 0.19                            | 0.17                             | 0.08                            | 0.57                            | 0.52                             | 0.23 |
| CWR11D^226^@+□                 | TBJC 226 * 006 C □ # @ 0 ^ ++ | TBJC 226 * 006 C □ L @ 9 ^ ++ | C   | 22                                  | 6                                  | 2.2     | 1.4   | 14    | 16.8   | 6     | 9     | 9                                 | 0.110                           | 0.22                            | 0.20                             | 0.09                            | 0.49                            | 0.44                             | 0.20 |
| CWR11D^476^@+□                 | TBJD 476 * 006 C □ # @ 0 ^ ++ | TBJD 476 * 006 C □ L @ 9 ^ ++ | D   | 47                                  | 6                                  | 1.1     | 2.8   | 28    | 33.6   | 6     | 9     | 9                                 | 0.150                           | 0.37                            | 0.33                             | 0.15                            | 0.41                            | 0.37                             | 0.16 |
| CWR11D^686^@+□                 | TBJD 686 * 006 C □ # @ 0 ^ ++ | TBJD 686 * 006 C □ L @ 9 ^ ++ | D   | 68                                  | 6                                  | 0.9     | 4.3   | 43    | 51.6   | 6     | 9     | 9                                 | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR11F^105^@+□                 | TBJA 105 * 010 C □ # @ 0 ^ ++ | TBJA 105 * 010 C □ L @ 9 ^ ++ | A   | 1                                   | 10                                 | 10      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.09                            | 0.08                             | 0.03                            | 0.87                            | 0.78                             | 0.35 |
| CWR11F^155^@+□                 | TBJA 155 * 010 C □ # @ 0 ^ ++ | TBJA 155 * 010 C □ L @ 9 ^ ++ | A   | 1.5                                 | 10                                 | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11F^225^@+□                 | TBJA 225 * 010 C □ # @ 0 ^ ++ | TBJA 225 * 010 C □ L @ 9 ^ ++ | A   | 2.2                                 | 10                                 | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11F^335^@+□                 | TBJB 335 * 010 C □ # @ 0 ^ ++ | TBJB 335 * 010 C □ L @ 9 ^ ++ | B   | 3.3                                 | 10                                 | 5.5     | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.12                            | 0.11                             | 0.05                            | 0.68                            | 0.62                             | 0.27 |
| CWR11F^475^@+□                 | TBJB 475 * 010 C □ # @ 0 ^ ++ | TBJB 475 * 010 C □ L @ 9 ^ ++ | B   | 4.7                                 | 10                                 | 4.5     | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.14                            | 0.12                             | 0.05                            | 0.62                            | 0.56                             | 0.25 |
| CWR11F^685^@+□                 | TBJB 685 * 010 C □ # @ 0 ^ ++ | TBJB 685 * 010 C □ L @ 9 ^ ++ | B   | 6.8                                 | 10                                 | 3.5     | 0.7   | 7     | 8.4    | 6     | 9     | 9                                 | 0.085                           | 0.16                            | 0.14                             | 0.06                            | 0.55                            | 0.49                             | 0.22 |
| CWR11F^156^@+□                 | TBJC 156 * 010 C □ # @ 0 ^ ++ | TBJC 156 * 010 C □ L @ 9 ^ ++ | C   | 15                                  | 10                                 | 2.5     | 1.5   | 15    | 18     | 6     | 6     | 9                                 | 0.110                           | 0.21                            | 0.19                             | 0.08                            | 0.52                            | 0.47                             | 0.21 |
| CWR11F^336^@+□                 | TBJD 336 * 010 C □ # @ 0 ^ ++ | TBJD 336 * 010 C □ L @ 9 ^ ++ | D   | 33                                  | 10                                 | 1.1     | 3.3   | 33    | 39.6   | 6     | 9     | 9                                 | 0.150                           | 0.37                            | 0.33                             | 0.15                            | 0.41                            | 0.37                             | 0.16 |
| CWR11F^476^@+□                 | TBJD 476 * 010 C □ # @ 0 ^ ++ | TBJD 476 * 010 C □ L @ 9 ^ ++ | D   | 47                                  | 10                                 | 0.9     | 4.7   | 47    | 56.4   | 6     | 9     | 9                                 | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR11H^684^@+□                 | TBJA 684 * 015 C □ # @ 0 ^ ++ | TBJA 684 * 015 C □ L @ 9 ^ ++ | A   | 0.68                                | 15                                 | 12      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.08                            | 0.07                             | 0.03                            | 0.95                            | 0.85                             | 0.38 |
| CWR11H^105^@+□                 | TBJA 105 * 015 C □ # @ 0 ^ ++ | TBJA 105 * 015 C □ L @ 9 ^ ++ | A   | 1                                   | 15                                 | 10      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.09                            | 0.08                             | 0.03                            | 0.87                            | 0.78                             | 0.35 |
| CWR11H^155^@+□                 | TBJA 155 * 015 C □ # @ 0 ^ ++ | TBJA 155 * 015 C □ L @ 9 ^ ++ | A   | 1.5                                 | 15                                 | 8       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.075                           | 0.10                            | 0.09                             | 0.04                            | 0.77                            | 0.70                             | 0.31 |
| CWR11H^225^@+□                 | TBJB 225 * 015 C □ # @ 0 ^ ++ | TBJB 225 * 015 C □ L @ 9 ^ ++ | B   | 2.2                                 | 15                                 | 5.5     | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.12                            | 0.11                             | 0.05                            | 0.68                            | 0.62                             | 0.27 |
| CWR11H^335^@+□                 | TBJB 335 * 015 C □ # @ 0 ^ ++ | TBJB 335 * 015 C □ L @ 9 ^ ++ | B   | 3.3                                 | 15                                 | 5       | 0.5   | 5     | 6      | 6     | 8     | 9                                 | 0.085                           | 0.13                            | 0.12                             | 0.05                            | 0.65                            | 0.59                             | 0.26 |
| CWR11H^475^@+□                 | TBJB 475 * 015 C □ # @ 0 ^ ++ | TBJB 475 * 015 C □ L @ 9 ^ ++ | B   | 4.7                                 | 15                                 | 4       | 0.7   | 7     | 8.4    | 6     | 9     | 9                                 | 0.085                           | 0.15                            | 0.13                             | 0.06                            | 0.58                            | 0.52                             | 0.23 |
| CWR11H^106^@+□                 | TBJC 106 * 015 C □ # @ 0 ^ ++ | TBJC 106 * 015 C □ L @ 9 ^ ++ | C   | 10                                  | 15                                 | 2.5     | 1.6   | 16    | 19.2   | 6     | 8     | 9                                 | 0.110                           | 0.21                            | 0.19                             | 0.08                            | 0.52                            | 0.47                             | 0.21 |
| CWR11H^226^@+□                 | TBJD 226 * 015 C □ # @ 0 ^ ++ | TBJD 226 * 015 C □ L @ 9 ^ ++ | D   | 22                                  | 15                                 | 1.1     | 3.3   | 33    | 39.6   | 6     | 8     | 9                                 | 0.150                           | 0.37                            | 0.33                             | 0.15                            | 0.41                            | 0.37                             | 0.16 |
| CWR11H^336^@+□                 | TBJD 336 * 015 C □ # @ 0 ^ ++ | TBJD 336 * 015 C □ L @ 9 ^ ++ | D   | 33                                  | 15                                 | 0.9     | 5.3   | 53    | 63.6   | 6     | 9     | 9                                 | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR11J^474^@+□                 | TBJA 474 * 020 C □ # @ 0 ^ ++ | TBJA 474 * 020 C □ L @ 9 ^ ++ | A   | 0.47                                | 20                                 | 14      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.07                            | 0.07                             | 0.03                            | 1.02                            | 0.92                             | 0.41 |
| CWR11J^684^@+□                 | TBJA 684 * 020 C □ # @ 0 ^ ++ | TBJA 684 * 020 C □ L @ 9 ^ ++ | A   | 0.68                                | 20                                 | 12      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.08                            | 0.07                             | 0.03                            | 0.95                            | 0.85                             | 0.38 |
| CWR11J^105^@+□                 | TBJA 105 * 020 C □ # @ 0 ^ ++ | TBJA 105 * 020 C □ L @ 9 ^ ++ | A   | 1                                   | 20                                 | 10      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.09                            | 0.08                             | 0.03                            | 0.87                            | 0.78                             | 0.35 |
| CWR11J^155^@+□                 | TBJB 155 * 020 C □ # @ 0 ^ ++ | TBJB 155 * 020 C □ L @ 9 ^ ++ | B   | 1.5                                 | 20                                 | 6       | 0.5   | 5     | 6      | 6     | 9     | 9                                 | 0.085                           | 0.12                            | 0.11                             | 0.05                            | 0.71                            | 0.64                             | 0.29 |
| CWR11J^225^@+□                 | TBJB 225 * 020 C □ # @ 0 ^ ++ | TBJB 225 * 020 C □ L @ 9 ^ ++ | B   | 2.2                                 | 20                                 | 5       | 0.5   | 5     | 6      | 6     | 8     | 9                                 | 0.085                           | 0.13                            | 0.12                             | 0.05                            | 0.65                            | 0.59                             | 0.26 |
| CWR11J^335^@+□                 | TBJB 335 * 020 C □ # @ 0 ^ ++ | TBJB 335 * 020 C □ L @ 9 ^ ++ | B   | 3.3                                 | 20                                 | 4       | 0.7   | 7     | 8.4    | 6     | 9     | 9                                 | 0.085                           | 0.15                            | 0.13                             | 0.06                            | 0.58                            | 0.52                             | 0.23 |
| CWR11J^475^@+□                 | TBJC 475 * 020 C □ # @ 0 ^ ++ | TBJC 475 * 020 C □ L @ 9 ^ ++ | C   | 4.7                                 | 20                                 | 3       | 1     | 10    | 12     | 6     | 8     | 9                                 | 0.110                           | 0.19                            | 0.17                             | 0.08                            | 0.57                            | 0.52                             | 0.23 |
| CWR11J^685^@+□                 | TBJC 685 * 020 C □ # @ 0 ^ ++ | TBJC 685 * 020 C □ L @ 9 ^ ++ | C   | 6.8                                 | 20                                 | 2.4     | 1.4   | 14    | 16.8   | 6     | 9     | 9                                 | 0.110                           | 0.21                            | 0.19                             | 0.09                            | 0.51                            | 0.46                             | 0.21 |
| CWR11J^156^@+□                 | TBJD 156 * 020 C □ # @ 0 ^ ++ | TBJD 156 * 020 C □ L @ 9 ^ ++ | D   | 15                                  | 20                                 | 1.1     | 3     | 30    | 36     | 6     | 8     | 9                                 | 0.150                           | 0.37                            | 0.33                             | 0.15                            | 0.41                            | 0.37                             | 0.16 |
| CWR11J^226^@+□                 | TBJD 226 * 020 C □ # @ 0 ^ ++ | TBJD 226 * 020 C □ L @ 9 ^ ++ | D   | 22                                  | 20                                 | 0.9     | 4.4   | 44    | 52.8   | 6     | 9     | 9                                 | 0.150                           | 0.41                            | 0.37                             | 0.16                            | 0.37                            | 0.33                             | 0.15 |
| CWR11K^334^@+□                 | TBJA 334 * 025 C □ # @ 0 ^ ++ | TBJA 334 * 025 C □ L @ 9 ^ ++ | A   | 0.33                                | 25                                 | 15      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.07                            | 0.06                             | 0.03                            | 1.06                            | 0.95                             | 0.42 |
| CWR11K^474^@+□                 | TBJA 474 * 025 C □ # @ 0 ^ ++ | TBJA 474 * 025 C □ L @ 9 ^ ++ | A   | 0.47                                | 25                                 | 14      | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.075                           | 0.07                            | 0.07                             | 0.03                            | 1.02                            | 0.92                             | 0.41 |
| CWR11K^684^@+□                 | TBJB 684 * 025 C □ # @ 0 ^ ++ | TBJB 684 * 025 C □ L @ 9 ^ ++ | B   | 0.68                                | 25                                 | 7.5     | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.085                           | 0.11                            | 0.10                             | 0.04                            | 0.80                            | 0.72                             | 0.32 |
| CWR11K^105^@+□                 | TBJB 105 * 025 C □ # @ 0 ^ ++ | TBJB 105 * 025 C □ L @ 9 ^ ++ | B   | 1                                   | 25                                 | 6.5     | 0.5   | 5     | 6      | 4     | 6     | 6                                 | 0.085                           | 0.11                            | 0.10                             | 0.05                            | 0.74                            | 0.67                             | 0.30 |
| CWR11K^155^@+□                 | TBJB 155 * 025 C □ # @ 0 ^ ++ | TBJB 155 * 025 C □ L @ 9 ^ ++ | B   | 1.5                                 | 25                                 | 6.5     | 0.5   | 5     | 6      | 6     | 8     | 9                                 | 0.085                           | 0.11                            | 0.10                             | 0.05                            | 0.74                            | 0.67                             | 0.30 |
| CWR11K^225^@+□                 | TBJC 225 * 025 C □ # @ 0 ^ ++ | TBJC 225 * 025 C □ L @ 9 ^ ++ | C   | 2.2                                 | 25                                 | 3.5     | 0.6   | 6     | 7.2    | 6     | 9     | 9                                 | 0.110                           | 0.18                            | 0.16                             | 0.07                            | 0.62                            | 0.56                             | 0.25 |
| CWR11K^335^@+□                 | TBJC 335 * 025 C □ # @ 0 ^ ++ | TBJC 335 * 025 C □ L @ 9 ^ ++ | C   | 3.3                                 | 25                                 | 3.5     | 0.9   | 9     | 10.8   | 6     | 8     | 9                                 | 0.110                           | 0.18                            | 0.16                             | 0.07                            | 0.62                            | 0.56                             | 0.25 |
| CWR11K^475^@+□                 | TBJC 475 * 025 C □ # @ 0 ^ ++ | TBJC 475 * 025 C □ L @ 9 ^ ++ | C   | 4.7                                 | 25                                 | 2.5     | 1.2   | 12    | 14.4   | 6     | 9     | 9                                 | 0.110                           | 0.21                            | 0.19                             | 0.08                            | 0.52                            | 0.47                             | 0.21 |
| CWR11K^685^@+□                 | TBJD 685 * 025 C □ # @ 0 ^ ++ | TBJD 685 * 025 C □ L @ 9 ^ ++ | D   | 6.8                                 | 25                                 | 1.4     | 1.7   | 17    | 20.4   | 6     | 9     | 9                                 | 0.150                           | 0.33                            | 0.29                             | 0.13                            | 0.46                            | 0.41                             | 0.18 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# TBJ Series



## CWR11 - MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                |      | Parametric Specifications by Rating per MIL-PRF-55365/8 |                               |                              |         |             |       |        |   |   | Typical RMS Ripple Data by Rating |                           |                           |                            |                           |                           |                            |
|--------------------------------|--------------------------------|--------------------------------|------|---|-------------------------------|------------------------------|---------|-------------|-------|--------|---|---|-----------------------------------|---------------------------|---------------------------|----------------------------|---------------------------|---------------------------|----------------------------|
|                                |                                |                                |      | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>Ohms @ +25°C | DCL max |             |       | DF Max |   |   | Power Dissipation<br>W            | 25°C Ripple<br>A (100kHz) | 85°C Ripple<br>A (100kHz) | 125°C Ripple<br>A (100kHz) | 25°C Ripple<br>V (100kHz) | 85°C Ripple<br>V (100kHz) | 125°C Ripple<br>V (100kHz) |
| CWR11 P/N                      | AVX COTS-Plus P/N              | AVX SRC9000 P/N                | Case | +25°C   | +85°C                         | +125°C                       | +25°C   | +(85/125)°C | -55°C |        |   |   |                                   |                           |                           |                            |                           |                           |                            |
| CWR11K^106^@+□                 | TBJ D 106 * 025 C □ # @ 0 ^ ++ | TBJ D 106 * 025 C □ L @ 9 ^ ++ | D    | 10  | 25                            | 1.2                          | 2.5     | 25          | 30    | 6      | 8 | 9 | 0.150                             | 0.35                      | 0.32                      | 0.14                       | 0.42                      | 0.38                      | 0.17                       |
| CWR11K^156^@+□                 | TBJ D 156 * 025 C □ # @ 0 ^ ++ | TBJ D 156 * 025 C □ L @ 9 ^ ++ | D    | 15  | 25                            | 1                            | 3.8     | 38          | 45.6  | 6      | 9 | 9 | 0.150                             | 0.39                      | 0.35                      | 0.15                       | 0.39                      | 0.35                      | 0.15                       |
| CWR11M^104^@+□                 | TBJ A 104 * 035 C □ # @ 0 ^ ++ | TBJ A 104 * 035 C □ L @ 9 ^ ++ | A    | 0.1   | 35                            | 24                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.075                             | 0.06                      | 0.05                      | 0.02                       | 1.34                      | 1.21                      | 0.54                       |
| CWR11M^154^@+□                 | TBJ A 154 * 035 C □ # @ 0 ^ ++ | TBJ A 154 * 035 C □ L @ 9 ^ ++ | A    | 0.15  | 35                            | 21                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.075                             | 0.06                      | 0.05                      | 0.02                       | 1.25                      | 1.13                      | 0.50                       |
| CWR11M^224^@+□                 | TBJ A 224 * 035 C □ # @ 0 ^ ++ | TBJ A 224 * 035 C □ L @ 9 ^ ++ | A    | 0.22  | 35                            | 18                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.075                             | 0.06                      | 0.06                      | 0.03                       | 1.16                      | 1.05                      | 0.46                       |
| CWR11M^334^@+□                 | TBJ A 334 * 035 C □ # @ 0 ^ ++ | TBJ A 334 * 035 C □ L @ 9 ^ ++ | A    | 0.33  | 35                            | 15                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.075                             | 0.07                      | 0.06                      | 0.03                       | 1.06                      | 0.95                      | 0.42                       |
| CWR11M^474^@+□                 | TBJ B 474 * 035 C □ # @ 0 ^ ++ | TBJ B 474 * 035 C □ L @ 9 ^ ++ | B    | 0.47  | 35                            | 10                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.085                             | 0.09                      | 0.08                      | 0.04                       | 0.92                      | 0.83                      | 0.37                       |
| CWR11M^684^@+□                 | TBJ B 684 * 035 C □ # @ 0 ^ ++ | TBJ B 684 * 035 C □ L @ 9 ^ ++ | B    | 0.68  | 35                            | 8                            | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.085                             | 0.10                      | 0.09                      | 0.04                       | 0.82                      | 0.74                      | 0.33                       |
| CWR11M^105^@+□                 | TBJ B 105 * 035 C □ # @ 0 ^ ++ | TBJ B 105 * 035 C □ L @ 9 ^ ++ | B    | 1   | 35                            | 6.5                          | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.085                             | 0.11                      | 0.10                      | 0.05                       | 0.74                      | 0.67                      | 0.30                       |
| CWR11M^155^@+□                 | TBJ C 155 * 035 C □ # @ 0 ^ ++ | TBJ C 155 * 035 C □ L @ 9 ^ ++ | C    | 1.5   | 35                            | 4.5                          | 0.5     | 5           | 6     | 6      | 8 | 9 | 0.110                             | 0.16                      | 0.14                      | 0.06                       | 0.70                      | 0.63                      | 0.28                       |
| CWR11M^225^@+□                 | TBJ C 225 * 035 C □ # @ 0 ^ ++ | TBJ C 225 * 035 C □ L @ 9 ^ ++ | C    | 2.2   | 35                            | 3.5                          | 0.8     | 8           | 9.6   | 6      | 8 | 9 | 0.110                             | 0.18                      | 0.16                      | 0.07                       | 0.62                      | 0.56                      | 0.25                       |
| CWR11M^335^@+□                 | TBJ C 335 * 035 C □ # @ 0 ^ ++ | TBJ C 335 * 035 C □ L @ 9 ^ ++ | C    | 3.3   | 35                            | 2.5                          | 1.2     | 12          | 14.4  | 6      | 8 | 9 | 0.110                             | 0.21                      | 0.19                      | 0.08                       | 0.52                      | 0.47                      | 0.21                       |
| CWR11M^475^@+□                 | TBJ D 475 * 035 C □ # @ 0 ^ ++ | TBJ D 475 * 035 C □ L @ 9 ^ ++ | D    | 4.7   | 35                            | 1.5                          | 1.7     | 17          | 20.4  | 6      | 8 | 9 | 0.150                             | 0.32                      | 0.28                      | 0.13                       | 0.47                      | 0.43                      | 0.19                       |
| CWR11M^685^@+□                 | TBJ D 685 * 035 C □ # @ 0 ^ ++ | TBJ D 685 * 035 C □ L @ 9 ^ ++ | D    | 6.8   | 35                            | 1.3                          | 2.4     | 24          | 28.8  | 6      | 9 | 9 | 0.150                             | 0.34                      | 0.31                      | 0.14                       | 0.44                      | 0.40                      | 0.18                       |
| CWR11N^104^@+□                 | TBJ A 104 * 050 C □ # @ 0 ^ ++ | TBJ A 104 * 050 C □ L @ 9 ^ ++ | A    | 0.1   | 50                            | 22                           | 0.5     | 5           | 12    | 6      | 8 | 8 | 0.075                             | 0.06                      | 0.05                      | 0.02                       | 1.28                      | 1.16                      | 0.51                       |
| CWR11N^154^@+□                 | TBJ B 154 * 050 C □ # @ 0 ^ ++ | TBJ B 154 * 050 C □ L @ 9 ^ ++ | B    | 0.15  | 50                            | 17                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.085                             | 0.07                      | 0.06                      | 0.03                       | 1.20                      | 1.08                      | 0.48                       |
| CWR11N^224^@+□                 | TBJ B 224 * 050 C □ # @ 0 ^ ++ | TBJ B 224 * 050 C □ L @ 9 ^ ++ | B    | 0.22  | 50                            | 14                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.085                             | 0.08                      | 0.07                      | 0.03                       | 1.09                      | 0.98                      | 0.44                       |
| CWR11N^334^@+□                 | TBJ B 334 * 050 C □ # @ 0 ^ ++ | TBJ B 334 * 050 C □ L @ 9 ^ ++ | B    | 0.33  | 50                            | 12                           | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.085                             | 0.08                      | 0.08                      | 0.03                       | 1.01                      | 0.91                      | 0.40                       |
| CWR11N^474^@+□                 | TBJ C 474 * 050 C □ # @ 0 ^ ++ | TBJ C 474 * 050 C □ L @ 9 ^ ++ | C    | 0.47  | 50                            | 8                            | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.110                             | 0.12                      | 0.11                      | 0.05                       | 0.94                      | 0.84                      | 0.38                       |
| CWR11N^684^@+□                 | TBJ C 684 * 050 C □ # @ 0 ^ ++ | TBJ C 684 * 050 C □ L @ 9 ^ ++ | C    | 0.68  | 50                            | 7                            | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.110                             | 0.13                      | 0.11                      | 0.05                       | 0.88                      | 0.79                      | 0.35                       |
| CWR11N^105^@+□                 | TBJ C 105 * 050 C □ # @ 0 ^ ++ | TBJ C 105 * 050 C □ L @ 9 ^ ++ | C    | 1   | 50                            | 6                            | 0.5     | 5           | 6     | 4      | 6 | 6 | 0.110                             | 0.14                      | 0.12                      | 0.05                       | 0.81                      | 0.73                      | 0.32                       |
| CWR11N^155^@+□                 | TBJ D 155 * 050 C □ # @ 0 ^ ++ | TBJ D 155 * 050 C □ L @ 9 ^ ++ | D    | 1.5   | 50                            | 4                            | 0.8     | 8           | 9.6   | 6      | 8 | 9 | 0.150                             | 0.19                      | 0.17                      | 0.08                       | 0.77                      | 0.70                      | 0.31                       |
| CWR11N^225^@+□                 | TBJ D 225 * 050 C □ # @ 0 ^ ++ | TBJ D 225 * 050 C □ L @ 9 ^ ++ | D    | 2.2   | 50                            | 2.5                          | 1.1     | 11          | 13.2  | 6      | 8 | 9 | 0.150                             | 0.24                      | 0.22                      | 0.10                       | 0.61                      | 0.55                      | 0.24                       |
| CWR11N^335^@+□                 | TBJ D 335 * 050 C □ # @ 0 ^ ++ | TBJ D 335 * 050 C □ L @ 9 ^ ++ | D    | 3.3   | 50                            | 2                            | 1.7     | 17          | 20.4  | 6      | 9 | 9 | 0.150                             | 0.27                      | 0.25                      | 0.11                       | 0.55                      | 0.49                      | 0.22                       |
| CWR11N^475^@+□                 | TBJ D 475 * 050 C □ # @ 0 ^ ++ | TBJ D 475 * 050 C □ L @ 9 ^ ++ | D    | 4.7   | 50                            | 1.5                          | 2.4     | 24          | 28.8  | 6      | 9 | 9 | 0.150                             | 0.32                      | 0.28                      | 0.13                       | 0.47                      | 0.43                      | 0.19                       |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# TBJ Series



## COTS-Plus




The TBJ COTS-Plus series, based on the CWR11 form factor, is a high reliability series encompassing the current range of EIA Low ESR ratings. These ratings are available with Weibull grading (B and C), surge current testing (A, B, C) per MIL-PRF-55365 Rev. G, and optional Group A from MIL-PRF-55365.

For Space Level applications, AVX SRC9000 qualification is recommended. Please refer to the TBJ COTS-Plus SRC9000 Datasheet for part number availability.

There are five termination finishes available: solder plated, fused solder plated, hot solder dipped, 100% Tin and gold plated (these correspond to "H", "K", "C", "7" and "B" termination, respectively). The molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.

### CASE DIMENSIONS: millimeters (inches)




| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|------------|----------------|------------------------------|------------------------------|------------------------------|------------------------------|--------------|
| A    | 1206     | 3216-18    | 3.20 (0.126)   | 1.60 (0.063)                 | 1.60 (0.063)                 | 1.20 (0.047)                 | 0.80 (0.031)                 | 1.10 (0.043) |
| B    | 1210     | 3528-21    | 3.50 (0.138)   | 2.80 (0.110)                 | 1.90 (0.075)                 | 2.20 (0.087)                 | 0.80 (0.031)                 | 1.40 (0.055) |
| C    | 2312     | 6032-28    | 6.00 (0.236)   | 3.20 (0.126)                 | 2.60 (0.102)                 | 2.20 (0.087)                 | 1.30 (0.051)                 | 2.90 (0.114) |
| D    | 2917     | 7343-31    | 7.30 (0.287)   | 4.30 (0.169)                 | 2.90 (0.114)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| E    | 2917     | 7343-43    | 7.30 (0.287)   | 4.30 (0.169)                 | 4.10 (0.162)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| V    | 2924     | 7361-38    | 7.30 (0.287)   | 6.10 (0.240)                 | 3.55 (0.140)                 | 3.10 (0.120)                 | 1.30 (0.051)                 | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### MARKING

#### A, B, C, D, E, V CASE



### HOW TO ORDER

#### AVX PART NUMBER:

| TBJ         | D                | 227  | *                            | 035  | C                          | B   | S                                   | Z   | 0                          | 0  | 00  |
|-------------|------------------|--|------------------------------|--|----------------------------|---|-------------------------------------|---|----------------------------|--|---|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b>  | <b>Capacitance Tolerance</b> | <b>Voltage Code</b>  | <b>ESR</b>                 | <b>Packaging</b>                                    | <b>Inspection Level</b>             | <b>Reliability Grade</b>  | <b>Qualification Level</b> | <b>Termination Finish</b>  | <b>Surge Test Option</b>  |
|             |                  | pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | K = ±10%<br>M = ±20%         | 002 = 2Vdc<br>004 = 4Vdc<br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | C = Std ESR<br>L = Low ESR | B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle | S = Std. Conformance<br>L = Group A | Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>Z = Non-ER | 0 = N/A                    | H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated<br>7 = Matte Sn | 00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |



For RoHS compliant products, please select correct termination style.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |     |   |    |    |    |    |    |    |  |
|------------------------------------|---|-----|-----|---|----|----|----|----|----|----|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |     |   |    |    |    |    |    |    |  |
| Capacitance Range:                 | 0.10 µF to 1500 µF  |     |     |   |    |    |    |    |    |    |  |
| Capacitance Tolerance:             | ±10%; ±20%  |     |     |   |    |    |    |    |    |    |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 2   | 4   | 6 | 10 | 16 | 20 | 25 | 35 | 50 |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 1.4 | 2.7 | 4 | 7  | 10 | 13 | 17 | 23 | 33 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 2.6 | 5.2 | 8 | 13 | 20 | 26 | 32 | 46 | 65 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 1.7 | 3.4 | 5 | 8  | 13 | 16 | 20 | 28 | 40 |  |
| Temperature Range:                 | -55°C to +125°C   |     |     |   |    |    |    |    |    |    |  |



### CAPACITANCE AND RATED VOLTAGE, $V_R$ (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance   |      | Rated Voltage DC ( $V_R$ ) to 85°C |                         |  |   |          |   |  |   |   |                            |
|---------------|------|------------------------------------|-------------------------|--|---|----------|---|--|---|---|----------------------------|
| $\mu\text{F}$ | Code | 2V                                 | 4V                      | 6V   | 10V   | 15V      | 16V   | 20V  | 25V                                     | 35V   | 50V                        |
| 0.10          | 104  |                                    |                         |  |   |          |   |  |   | A(24000)  | A(22000)                   |
| 0.15          | 154  |                                    |                         |  |   |          |   |  |   | A(21000)  | A(9000, 21000)<br>B(17000) |
| 0.22          | 224  |                                    |                         |  |   |          |   |  |   | A(6000, 18000)                                  | A(7000, 18000)<br>B(14000) |
| 0.33          | 334  |                                    |                         |  |   |          |   |  |   | A(6000, 15000)                                  | B(12000)                   |
| 0.47          | 474  |                                    |                         |  |   |          |   | A(14000)                                   | A(7000, 14000)                          | A(6000, 12000)<br>B(4000, 10000)                | C(8000)                    |
| 0.68          | 684  |                                    |                         |  |   | A(12000) | A(12000)                                      | A(12000)                                   | A(6000, 10000)<br>B(7500)               | A(6000, 8000)<br>B(8000)                        | A(7900)<br>C(7000)         |
| 1.0           | 105  |                                    |                         |  | A(10000)  | A(10000) | A(10000)                                      | A(3000, 10000)                             | A(8000)<br>B(6500)                      | A(3000, 7500)<br>B(2000, 6500)                  | C(2500, 6000)              |
| 1.5           | 155  |                                    |                         | A(8000)  | A(8000)   | A(8000)  |   | A(6500)<br>B(6000)                         | A(3000, 7500)<br>B(1800, 6500)          | A(7500)<br>B(2500, 5200)<br>C(4500)             | C(1500, 5000)<br>D(4000)   |
| 2.2           | 225  |                                    | A(8000)                 | A(8000)  | A(1800, 8000)   | B(5500)  | A(1800, 5500)<br>B(5000)                      | A(3000, 5300)<br>B(5000)                   | A(7000)<br>B(900, 4500)<br>C(3500)      | A(1500, 4500)<br>B(2000, 4200)<br>C(1000, 3500) | D(1200, 2500)              |
| 3.3           | 335  |                                    |                         | A(8000)  | B(5500)   | B(5000)  | A(3500, 5000)<br>B(4500)                      | A(2500)<br>B(1300, 4000)                   | A(2800)<br>B(750, 3500)<br>C(3500)      | B(1000, 3500)<br>C(700, 2500)                   | D(800, 2000)               |
| 4.7           | 475  |                                    | A(8000)                 | B(5500)  | A(1400, 5000)<br>B(4500)                                | B(4000)  | A(2000, 4000)<br>B(800, 3100)                 | A(1800, 4000)<br>B(750, 3000)<br>C(3000)   | A(2800)<br>B(1500, 2300)<br>C(2500)     | B(700, 3100)<br>C(600, 2200)<br>D(500, 1500)    | D(300, 1500)               |
| 6.8           | 685  |                                    | B(5500)                 | A(1800, 5000)<br>B(4500)                         | A(1800, 4000)<br>B(3500)                                |          | A(1500, 2500)<br>B(60, 2500)                  | A(1000)<br>B(600, 2500)<br>C(700, 2400)    | B(700, 2800)<br>C(500, 2000)<br>D(1400) | C(350, 1800)<br>D(500, 1300)                    | D(500, 1000)               |
| 10            | 106  |                                    | B(4000)                 | A(1500, 4000)<br>B(3500)                         | A(1800, 3000)<br>B(2500)                                | C(2500)  | A(1000, 3000)<br>B(500, 2800)<br>C(500, 2500) | B(1000, 2100)<br>C(500, 1900)              | C(500, 1800)<br>D(1200)                 | C(600, 1600)<br>D(300, 1000)<br>E(200, 250)     | E(400, 500)<br>V(650)      |
| 15            | 156  |                                    | B(3500)                 | A(1500, 3500)<br>B(3500)<br>C(3000)              | A(1000, 3200)<br>B(450, 2800)<br>C(2500)                |          | B(800, 2500)<br>C(1800)                       | B(500, 2000)<br>C(400, 1700)<br>D(1100)    | C(220, 300)<br>D(300, 1000)             | C(350, 1400)<br>D(300, 900)                     | D(600)<br>E(250, 600)      |
| 22            | 226  |                                    |                         | A(500, 3000)<br>B(375, 2500)<br>C(2200)          | B(700, 2400)<br>C(300, 1000)                            | D(1100)  | B(600, 2300)<br>C(375, 1600)<br>D(1100)       | B(400, 600)<br>C(150, 1600)<br>D(200, 900) | C(275, 1400)<br>D(200, 900)             | D(400, 900)<br>E(300, 900)                      | V(390, 600)                |
| 33            | 336  |                                    | A(3000)<br>C(2200)      | A(600)<br>B(600, 2200)                           | A(700, 1700)<br>B(250, 1800)<br>C(150, 1600)<br>D(1100) | D(900)   | B(350)<br>C(300, 1500)<br>D(200, 900)         | C(300, 1500)<br>D(100, 900)                | D(100, 900)<br>E(300, 900)              | D(300, 900)<br>E(100, 250)<br>V(200)            |                            |
| 47            | 476  |                                    | A(500)                  | A(800)<br>B(250, 350)<br>C(300, 1600)<br>D(1100) | B(250, 350)<br>C(200, 1200)<br>D(100, 900)              |          | C(350, 1500)<br>D(150, 900)                   | D(100, 200)<br>E(70, 250)                  | D(250, 900)<br>E(80, 100)               | E(200, 250)<br>V(200, 400)                      |                            |
| 68            | 686  |                                    | D(1100)                 | B(250, 1800)<br>C(150, 1600)<br>D(900)           | B(600)<br>C(80, 1200)<br>D(100, 900)                    |          | C(125, 200)<br>D(70, 900)                     | D(70, 900)<br>E(150, 900)                  | E(125, 200)<br>V(95)                    | V(150, 200)                                     |                            |
| 100           | 107  |                                    | A(1400)<br>B(200, 1600) | B(250, 400)<br>C(150, 900)<br>D(900)             | B(400)<br>C(200, 1200)<br>D(100, 900)<br>E(125)         |          | D(125, 900)<br>E(100, 900)                    | D(85, 100)<br>E(100, 150)<br>V(85, 200)    | V(100)                                  |   |                            |
| 150           | 157  | B(150)                             | B(250)<br>C(70, 80)     | C(50, 90)<br>D(50, 900)                          | D(150, 900)<br>E(100)                                   |          | D(150, 900)<br>E(100, 300)<br>V(45, 75)       | E(300)<br>V(80)                            |   |   |                            |
| 220           | 227  | B(150, 200)<br>D(45)               | D(40, 900)              | C(70, 1200)<br>D(100, 900)<br>E(100)             | D(150, 900)<br>E(100, 900)                              |          | E(100, 150)<br>V(75, 150)                     |  |   |   |                            |
| 330           | 337  |                                    | C(100)<br>D(35, 45)     | D(45, 50)<br>E(100, 900)<br>V(100)               | D(150, 900)<br>E(60, 900)<br>V(60, 100)                 |          |   |  |   |   |                            |
| 470           | 477  | D(35)                              | D(45, 100)<br>E(35)     | D(45, 60)<br>E(50, 900)<br>V(55, 100)            | E(50, 900)<br>V(60, 100)                                |          |   |  |   |   |                            |
| 680           | 687  | D(35, 50)<br>E(35, 50)             | D(45, 60)<br>E(40, 60)  | E(45, 60)<br>V(35, 40)                           |   |          |   |  |   |   |                            |
| 1000          | 108  | E(30, 40)                          | E(60)<br>V(25, 35)      | V(40, 50)  |   |          |   |  |   |   |                            |
| 1500          | 158  | D(100)<br>E(50)<br>V(30, 40)       | E(50, 75)<br>V(50, 75)  |  |   |          |   |  |   |   |                            |

Available Ratings: ESR limits quoted in brackets (mOhms)

Not recommended for new designs, higher voltage or smaller case size substitution are offered.

Notes: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards.



# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                              |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |                  |              | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                              | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJB157*002L□#@0^++            | B | 150   | 2                             | 0.15                         | 3             | 30            | 60             | 10           | 12               | 14           | 0.085                             | 0.753                                | 0.677                                | 0.301                                 | 0.113                                | 0.102                                | 0.045                                 |
| TBJB227*002C□#@0^++            | B | 220   | 2                             | 0.2                          | 4.4           | 44            | 88             | 16           | 19               | 21           | 0.085                             | 0.652                                | 0.587                                | 0.261                                 | 0.130                                | 0.117                                | 0.052                                 |
| TBJB227*002L□#@0^++            | B | 220   | 2                             | 0.15                         | 4.4           | 44            | 88             | 16           | 19               | 21           | 0.085                             | 0.753                                | 0.677                                | 0.301                                 | 0.113                                | 0.102                                | 0.045                                 |
| TBJD227*002L□#@0^++            | D | 220   | 2                             | 0.045                        | 4.4           | 44            | 88             | 8            | 10               | 12           | 0.150                             | 1.826                                | 1.643                                | 0.730                                 | 0.082                                | 0.074                                | 0.033                                 |
| TBJD477*002L□#@0^++            | D | 470   | 2                             | 0.035                        | 9.4           | 94            | 188            | 8            | 10               | 12           | 0.150                             | 2.070                                | 1.863                                | 0.828                                 | 0.072                                | 0.065                                | 0.029                                 |
| TBJD687*002C□#@0^++            | D | 680   | 2                             | 0.05                         | 13.6          | 136           | 272            | 16           | 19               | 21           | 0.150                             | 1.732                                | 1.559                                | 0.693                                 | 0.087                                | 0.078                                | 0.035                                 |
| TBJD687*002L□#@0^++            | D | 680   | 2                             | 0.035                        | 13.6          | 136           | 272            | 16           | 19               | 21           | 0.150                             | 2.070                                | 1.863                                | 0.828                                 | 0.072                                | 0.065                                | 0.029                                 |
| TBJE687*002C□#@0^++            | E | 680   | 2                             | 0.05                         | 13.6          | 136           | 272            | 10           | 12               | 14           | 0.165                             | 1.817                                | 1.635                                | 0.727                                 | 0.091                                | 0.082                                | 0.036                                 |
| TBJE687*002L□#@0^++            | E | 680   | 2                             | 0.035                        | 13.6          | 136           | 272            | 10           | 12               | 14           | 0.165                             | 2.171                                | 1.954                                | 0.868                                 | 0.076                                | 0.068                                | 0.030                                 |
| TBJE108*002C□#@0^++            | E | 1000  | 2                             | 0.04                         | 20            | 200           | 400            | 14           | 17               | 20           | 0.165                             | 2.031                                | 1.828                                | 0.812                                 | 0.081                                | 0.073                                | 0.032                                 |
| TBJE108*002L□#@0^++            | E | 1000  | 2                             | 0.03                         | 20            | 200           | 400            | 14           | 17               | 20           | 0.165                             | 2.345                                | 2.111                                | 0.938                                 | 0.070                                | 0.063                                | 0.028                                 |
| TBJD158*002L□#@0^++            | D | 1500  | 2                             | 0.1                          | 30            | 300           | 600            | 60           | 90               | 90           | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJE158*002L□#@0^++            | E | 1500  | 2                             | 0.05                         | 30            | 300           | 600            | 20           | 24               | 28           | 0.165                             | 1.817                                | 1.635                                | 0.727                                 | 0.091                                | 0.082                                | 0.036                                 |
| TBJV158*002C□#@0^++            | V | 1500  | 2                             | 0.04                         | 30            | 300           | 600            | 20           | 24               | 28           | 0.250                             | 2.500                                | 2.250                                | 1.000                                 | 0.100                                | 0.090                                | 0.040                                 |
| TBJV158*002L□#@0^++            | V | 1500  | 2                             | 0.03                         | 30            | 300           | 600            | 20           | 24               | 28           | 0.250                             | 2.887                                | 2.598                                | 1.155                                 | 0.087                                | 0.078                                | 0.035                                 |
| TBJA225*004C□#@0^++            | A | 2.2   | 4                             | 8                            | 0.088         | 0.88          | 1.76           | 6            | 9                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJA475*004C□#@0^++            | A | 4.7   | 4                             | 8                            | 0.188         | 1.88          | 3.76           | 6            | 9                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJB685*004C□#@0^++            | B | 6.8   | 4                             | 5.5                          | 0.272         | 2.72          | 5.44           | 6            | 9                | 9            | 0.085                             | 0.124                                | 0.112                                | 0.050                                 | 0.684                                | 0.615                                | 0.273                                 |
| TBJB106*004C□#@0^++            | B | 10  | 4                             | 4                            | 0.4           | 4             | 8              | 6            | 9                | 9            | 0.085                             | 0.146                                | 0.131                                | 0.058                                 | 0.583                                | 0.525                                | 0.233                                 |
| TBJB156*004C□#@0^++            | B | 15  | 4                             | 3.5                          | 0.6           | 6             | 12             | 6            | 9                | 9            | 0.085                             | 0.156                                | 0.140                                | 0.062                                 | 0.545                                | 0.491                                | 0.218                                 |
| TBJA336*004C□#@0^++            | A | 33  | 4                             | 3                            | 1.32          | 13.2          | 26.4           | 6            | 9                | 9            | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJC336*004C□#@0^++            | C | 33  | 4                             | 2.2                          | 1.32          | 13.2          | 26.4           | 6            | 9                | 9            | 0.110                             | 0.224                                | 0.201                                | 0.089                                 | 0.492                                | 0.443                                | 0.197                                 |
| TBJA476*004L□#@0^++            | A | 47  | 4                             | 0.5                          | 1.88          | 18.8          | 37.6           | 8            | 10               | 12           | 0.075                             | 0.387                                | 0.349                                | 0.155                                 | 0.194                                | 0.174                                | 0.077                                 |
| TBJC686*004C□#@0^++            | C | 68  | 4                             | 1.6                          | 2.72          | 27.2          | 54.4           | 6            | 9                | 10           | 0.110                             | 0.262                                | 0.236                                | 0.105                                 | 0.420                                | 0.378                                | 0.168                                 |
| TBJD686*004C□#@0^++            | D | 68  | 4                             | 1.1                          | 2.72          | 27.2          | 54.4           | 6            | 9                | 9            | 0.150                             | 0.369                                | 0.332                                | 0.148                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJA107*004C□#@0^++            | A | 100   | 4                             | 1.4                          | 4             | 40            | 80             | 30           | 36               | 42           | 0.075                             | 0.231                                | 0.208                                | 0.093                                 | 0.324                                | 0.292                                | 0.130                                 |
| TBJB107*004C□#@0^++            | B | 100   | 4                             | 1.6                          | 4             | 40            | 80             | 8            | 10               | 12           | 0.085                             | 0.230                                | 0.207                                | 0.092                                 | 0.369                                | 0.332                                | 0.148                                 |
| TBJB107*004L□#@0^++            | B | 100   | 4                             | 0.2                          | 4             | 40            | 80             | 8            | 10               | 12           | 0.085                             | 0.652                                | 0.587                                | 0.261                                 | 0.130                                | 0.117                                | 0.052                                 |
| TBJB157*004L□#@0^++            | B | 150   | 4                             | 0.25                         | 6             | 60            | 120            | 10           | 12               | 12           | 0.085                             | 0.583                                | 0.525                                | 0.233                                 | 0.146                                | 0.131                                | 0.058                                 |
| TBJC157*004C□#@0^++            | C | 150   | 4                             | 0.08                         | 6             | 60            | 120            | 6            | 9                | 10           | 0.110                             | 1.173                                | 1.055                                | 0.469                                 | 0.094                                | 0.084                                | 0.038                                 |
| TBJC157*004L□#@0^++            | C | 150   | 4                             | 0.07                         | 6             | 60            | 120            | 6            | 9                | 10           | 0.110                             | 1.254                                | 1.128                                | 0.501                                 | 0.088                                | 0.079                                | 0.035                                 |
| TBJD227*004C□#@0^++            | D | 220   | 4                             | 0.9                          | 8.8           | 88            | 176            | 8            | 10               | 12           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD227*004L□#@0^++            | D | 220   | 4                             | 0.04                         | 8.8           | 88            | 176            | 8            | 10               | 12           | 0.150                             | 1.936                                | 1.743                                | 0.775                                 | 0.077                                | 0.070                                | 0.031                                 |
| TBJC337*004L□#@0^++            | C | 330   | 4                             | 0.1                          | 13.2          | 132           | 264            | 8            | 10               | 12           | 0.110                             | 1.049                                | 0.944                                | 0.420                                 | 0.105                                | 0.094                                | 0.042                                 |
| TBJD337*004C□#@0^++            | D | 330   | 4                             | 0.045                        | 13.2          | 132           | 264            | 8            | 10               | 12           | 0.150                             | 1.826                                | 1.643                                | 0.730                                 | 0.082                                | 0.074                                | 0.033                                 |
| TBJD337*004L□#@0^++            | D | 330   | 4                             | 0.035                        | 13.2          | 132           | 264            | 8            | 10               | 12           | 0.150                             | 2.070                                | 1.863                                | 0.828                                 | 0.072                                | 0.065                                | 0.029                                 |
| TBJD477*004C□#@0^++            | D | 470   | 4                             | 0.1                          | 18.8          | 188           | 376            | 12           | 14               | 16           | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJD477*004L□#@0^++            | D | 470   | 4                             | 0.045                        | 18.8          | 188           | 376            | 12           | 14               | 16           | 0.150                             | 1.826                                | 1.643                                | 0.730                                 | 0.082                                | 0.074                                | 0.033                                 |
| TBJE477*004L□#@0^++            | E | 470   | 4                             | 0.035                        | 18.8          | 188           | 376            | 12           | 14               | 16           | 0.165                             | 2.171                                | 1.954                                | 0.868                                 | 0.076                                | 0.068                                | 0.030                                 |
| TBJD687*004C□#@0^++            | D | 680   | 4                             | 0.06                         | 27.2          | 272           | 544            | 14           | 17               | 20           | 0.150                             | 1.581                                | 1.423                                | 0.632                                 | 0.095                                | 0.085                                | 0.038                                 |
| TBJD687*004L□#@0^++            | D | 680   | 4                             | 0.045                        | 27.2          | 272           | 544            | 14           | 17               | 20           | 0.150                             | 1.826                                | 1.643                                | 0.730                                 | 0.082                                | 0.074                                | 0.033                                 |
| TBJE687*004C□#@0^++            | E | 680   | 4                             | 0.06                         | 27.2          | 272           | 544            | 10           | 12               | 14           | 0.165                             | 1.658                                | 1.492                                | 0.663                                 | 0.099                                | 0.090                                | 0.040                                 |
| TBJE687*004L□#@0^++            | E | 680   | 4                             | 0.04                         | 27.2          | 272           | 544            | 10           | 12               | 14           | 0.165                             | 2.031                                | 1.828                                | 0.812                                 | 0.081                                | 0.073                                | 0.032                                 |
| TBJE108*004L□#@0^++            | E | 1000  | 4                             | 0.06                         | 40            | 400           | 800            | 14           | 17               | 20           | 0.165                             | 1.658                                | 1.492                                | 0.663                                 | 0.099                                | 0.090                                | 0.040                                 |
| TBJV108*004C□#@0^++            | V | 1000  | 4                             | 0.035                        | 40            | 400           | 800            | 16           | 19               | 21           | 0.250                             | 2.673                                | 2.405                                | 1.069                                 | 0.094                                | 0.084                                | 0.037                                 |
| TBJV108*004L□#@0^++            | V | 1000  | 4                             | 0.025                        | 40            | 400           | 800            | 16           | 18               | 20           | 0.250                             | 3.162                                | 2.846                                | 1.265                                 | 0.079                                | 0.071                                | 0.032                                 |
| TBJE158*004C□#@0^++            | E | 1500  | 4                             | 0.075                        | 60            | 600           | 1200           | 30           | 36               | 42           | 0.165                             | 1.483                                | 1.335                                | 0.593                                 | 0.111                                | 0.100                                | 0.044                                 |
| TBJE158*004L□#@0^++            | E | 1500  | 4                             | 0.05                         | 60            | 600           | 1200           | 30           | 36               | 42           | 0.165                             | 1.817                                | 1.635                                | 0.727                                 | 0.091                                | 0.082                                | 0.036                                 |
| TBJV158*004C□#@0^++            | V | 1500  | 4                             | 0.075                        | 60            | 600           | 1200           | 30           | 36               | 42           | 0.250                             | 1.826                                | 1.643                                | 0.730                                 | 0.137                                | 0.123                                | 0.055                                 |
| TBJV158*004L□#@0^++            | V | 1500  | 4                             | 0.05                         | 60            | 600           | 1200           | 30           | 36               | 42           | 0.250                             | 2.236                                | 2.012                                | 0.894                                 | 0.112                                | 0.101                                | 0.045                                 |
| TBJA155*006C□#@0^++            | A | 1.5   | 6                             | 8                            | 0.09          | 0.9           | 1.08           | 6            | 9                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJA225*006C□#@0^++            | A | 2.2   | 6                             | 8                            | 0.132         | 1.32          | 1.584          | 6            | 9                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJA335*006C□#@0^++            | A | 3.3   | 6                             | 8                            | 0.198         | 1.98          | 2.376          | 6            | 9                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJB475*006C□#@0^++            | B | 4.7   | 6                             | 5.5                          | 0.282         | 2.82          | 3.384          | 6            | 9                | 9            | 0.085                             | 0.124                                | 0.112                                | 0.050                                 | 0.684                                | 0.615                                | 0.273                                 |
| TBJA685*006C□#@0^++            | A | 6.8   | 6                             | 5                            | 0.408         | 4.08          | 8.16           | 6            | 9                | 10           | 0.075                             | 0.122                                | 0.110                                | 0.049                                 | 0.612                                | 0.551                                | 0.245                                 |
| TBJA685*006L□#@0^++            | A | 6.8   | 6                             | 1.8                          | 0.408         | 4.08          | 8.16           | 6            | 9                | 10           | 0.075                             | 0.204                                | 0.184                                | 0.082                                 | 0.367                                | 0.331                                | 0.147                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                              |               |               |                |              |              |               | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|------------------------------|---------------|---------------|----------------|--------------|--------------|---------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |              |               | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                              | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85°C<br>(%) | +125°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJB685*006C□#@0^++            | B | 6.8   | 6                             | 4.5                          | 0.408         | 4.08          | 4.896          | 6            | 9            | 9             | 0.085                             | 0.137                                | 0.124                                | 0.055                                 | 0.618                                | 0.557                                | 0.247                                 |
| TBJA106*006C□#@0^++            | A | 10  | 6                             | 4                            | 0.6           | 6             | 12             | 6            | 9            | 10            | 0.075                             | 0.137                                | 0.123                                | 0.055                                 | 0.548                                | 0.493                                | 0.219                                 |
| TBJA106*006L□#@0^++            | A | 10  | 6                             | 1.5                          | 0.6           | 6             | 12             | 6            | 9            | 10            | 0.075                             | 0.224                                | 0.201                                | 0.089                                 | 0.335                                | 0.302                                | 0.134                                 |
| TBJB106*006C□#@0^++            | B | 10  | 6                             | 3.5                          | 0.6           | 6             | 7.2            | 6            | 9            | 9             | 0.085                             | 0.156                                | 0.140                                | 0.062                                 | 0.545                                | 0.491                                | 0.218                                 |
| TBJA156*006C□#@0^++            | A | 15  | 6                             | 3.5                          | 0.9           | 9             | 18             | 6            | 9            | 10            | 0.075                             | 0.146                                | 0.132                                | 0.059                                 | 0.512                                | 0.461                                | 0.205                                 |
| TBJA156*006L□#@0^++            | A | 15  | 6                             | 1.5                          | 0.9           | 9             | 18             | 6            | 9            | 10            | 0.075                             | 0.224                                | 0.201                                | 0.089                                 | 0.335                                | 0.302                                | 0.134                                 |
| TBJB156*006C□#@0^++            | B | 15  | 6                             | 3.5                          | 0.225         | 2.25          | 4.5            | 6            | 9            | 10            | 0.085                             | 0.156                                | 0.140                                | 0.062                                 | 0.545                                | 0.491                                | 0.218                                 |
| TBJC156*006C□#@0^++            | C | 15  | 6                             | 3                            | 0.9           | 9             | 10.8           | 6            | 9            | 9             | 0.110                             | 0.191                                | 0.172                                | 0.077                                 | 0.574                                | 0.517                                | 0.230                                 |
| TBJA226*006C□#@0^++            | A | 22  | 6                             | 3                            | 1.32          | 13.2          | 26.4           | 6            | 6            | 10            | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJA226*006L□#@0^++            | A | 22  | 6                             | 0.5                          | 1.32          | 13.2          | 26.4           | 6            | 9            | 10            | 0.075                             | 0.387                                | 0.349                                | 0.155                                 | 0.194                                | 0.174                                | 0.077                                 |
| TBJB226*006C□#@0^++            | B | 22  | 6                             | 2.5                          | 1.32          | 13.2          | 26.4           | 6            | 9            | 10            | 0.085                             | 0.184                                | 0.166                                | 0.074                                 | 0.461                                | 0.415                                | 0.184                                 |
| TBJB226*006L□#@0^++            | B | 22  | 6                             | 0.375                        | 1.32          | 13.2          | 26.4           | 6            | 9            | 10            | 0.085                             | 0.476                                | 0.428                                | 0.190                                 | 0.179                                | 0.161                                | 0.071                                 |
| TBJC226*006C□#@0^++            | C | 22  | 6                             | 2.2                          | 1.32          | 13.2          | 15.84          | 6            | 9            | 9             | 0.110                             | 0.224                                | 0.201                                | 0.089                                 | 0.492                                | 0.443                                | 0.197                                 |
| TBJA336*006L□#@0^++            | A | 33  | 6                             | 0.6                          | 1.98          | 19.8          | 39.6           | 8            | 10           | 12            | 0.075                             | 0.354                                | 0.318                                | 0.141                                 | 0.212                                | 0.191                                | 0.085                                 |
| TBJB336*006C□#@0^++            | B | 33  | 6                             | 2.2                          | 1.98          | 19.8          | 39.6           | 6            | 9            | 10            | 0.085                             | 0.197                                | 0.177                                | 0.079                                 | 0.432                                | 0.389                                | 0.173                                 |
| TBJB336*006L□#@0^++            | B | 33  | 6                             | 0.6                          | 1.98          | 19.8          | 39.6           | 6            | 9            | 10            | 0.085                             | 0.376                                | 0.339                                | 0.151                                 | 0.226                                | 0.203                                | 0.090                                 |
| TBJA476*006L□#@0^++            | A | 47  | 6                             | 0.8                          | 2.82          | 28.2          | 56.4           | 10           | 12           | 14            | 0.075                             | 0.306                                | 0.276                                | 0.122                                 | 0.245                                | 0.220                                | 0.098                                 |
| TJB476*006C□#@0^++             | B | 47  | 6                             | 0.35                         | 2.82          | 28.2          | 56.4           | 6            | 9            | 10            | 0.085                             | 0.493                                | 0.444                                | 0.197                                 | 0.172                                | 0.155                                | 0.069                                 |
| TJB476*006L□#@0^++             | B | 47  | 6                             | 0.25                         | 2.82          | 28.2          | 56.4           | 6            | 9            | 10            | 0.085                             | 0.583                                | 0.525                                | 0.233                                 | 0.146                                | 0.131                                | 0.058                                 |
| TBJC476*006C□#@0^++            | C | 47  | 6                             | 1.6                          | 2.82          | 28.2          | 56.4           | 6            | 9            | 10            | 0.110                             | 0.262                                | 0.236                                | 0.105                                 | 0.420                                | 0.378                                | 0.168                                 |
| TBJC476*006L□#@0^++            | C | 47  | 6                             | 0.3                          | 2.82          | 28.2          | 56.4           | 6            | 9            | 10            | 0.110                             | 0.606                                | 0.545                                | 0.242                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJD476*006C□#@0^++            | D | 47  | 6                             | 1.1                          | 2.82          | 28.2          | 33.84          | 6            | 6            | 9             | 0.150                             | 0.369                                | 0.332                                | 0.148                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJB686*006C□#@0^++            | B | 68  | 6                             | 1.8                          | 4.08          | 40.8          | 81.6           | 8            | 10           | 12            | 0.085                             | 0.217                                | 0.196                                | 0.087                                 | 0.391                                | 0.352                                | 0.156                                 |
| TBJB686*006L□#@0^++            | B | 68  | 6                             | 0.25                         | 4.08          | 40.8          | 81.6           | 8            | 9            | 10            | 0.085                             | 0.583                                | 0.525                                | 0.233                                 | 0.146                                | 0.131                                | 0.058                                 |
| TBJC686*006C□#@0^++            | C | 68  | 6                             | 1.6                          | 4.08          | 40.8          | 81.6           | 6            | 9            | 10            | 0.110                             | 0.262                                | 0.236                                | 0.105                                 | 0.420                                | 0.378                                | 0.168                                 |
| TBJC686*006L□#@0^++            | C | 68  | 6                             | 0.15                         | 4.08          | 40.8          | 81.6           | 6            | 9            | 10            | 0.110                             | 0.856                                | 0.771                                | 0.343                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD686*006C□#@0^++            | D | 68  | 6                             | 0.9                          | 4.08          | 40.8          | 48.96          | 6            | 9            | 9             | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJB107*006C□#@0^++            | B | 100   | 6                             | 0.4                          | 6             | 60            | 120            | 10           | 12           | 14            | 0.085                             | 0.461                                | 0.415                                | 0.184                                 | 0.184                                | 0.166                                | 0.074                                 |
| TBJB107*006L□#@0^++            | B | 100   | 6                             | 0.25                         | 6             | 60            | 120            | 10           | 12           | 14            | 0.085                             | 0.583                                | 0.525                                | 0.233                                 | 0.146                                | 0.131                                | 0.058                                 |
| TBJC107*006C□#@0^++            | C | 100   | 6                             | 0.9                          | 6             | 60            | 120            | 6            | 9            | 10            | 0.110                             | 0.350                                | 0.315                                | 0.140                                 | 0.315                                | 0.283                                | 0.126                                 |
| TBJC107*006L□#@0^++            | C | 100   | 6                             | 0.15                         | 6             | 60            | 120            | 6            | 9            | 10            | 0.110                             | 0.856                                | 0.771                                | 0.343                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD107*006C□#@0^++            | D | 100   | 6                             | 0.9                          | 6             | 60            | 120            | 6            | 9            | 10            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJC157*006C□#@0^++            | C | 150   | 6                             | 0.09                         | 9             | 90            | 180            | 6            | 9            | 10            | 0.110                             | 1.106                                | 0.995                                | 0.442                                 | 0.099                                | 0.090                                | 0.040                                 |
| TBJC157*006L□#@0^++            | C | 150   | 6                             | 0.05                         | 9             | 90            | 180            | 6            | 9            | 10            | 0.110                             | 1.483                                | 1.335                                | 0.593                                 | 0.074                                | 0.067                                | 0.030                                 |
| TBJD157*006C□#@0^++            | D | 150   | 6                             | 0.9                          | 9             | 90            | 180            | 6            | 9            | 10            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD157*006L□#@0^++            | D | 150   | 6                             | 0.05                         | 9             | 90            | 180            | 6            | 9            | 10            | 0.150                             | 1.732                                | 1.559                                | 0.693                                 | 0.087                                | 0.078                                | 0.035                                 |
| TBJC227*006C□#@0^++            | C | 220   | 6                             | 1.2                          | 13.2          | 132           | 264            | 10           | 12           | 14            | 0.110                             | 0.303                                | 0.272                                | 0.121                                 | 0.363                                | 0.327                                | 0.145                                 |
| TBJC227*006L□#@0^++            | C | 220   | 6                             | 0.07                         | 13.2          | 132           | 264            | 8            | 10           | 12            | 0.110                             | 1.254                                | 1.128                                | 0.501                                 | 0.088                                | 0.079                                | 0.035                                 |
| TBJD227*006C□#@0^++            | D | 220   | 6                             | 0.9                          | 13.2          | 132           | 264            | 8            | 10           | 12            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD227*006L□#@0^++            | D | 220   | 6                             | 0.1                          | 13.2          | 132           | 264            | 8            | 10           | 12            | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJE227*006L□#@0^++            | E | 220   | 6                             | 0.1                          | 13.2          | 132           | 264            | 8            | 10           | 12            | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD337*006C□#@0^++            | D | 330   | 6                             | 0.05                         | 19.8          | 198           | 396            | 8            | 10           | 12            | 0.150                             | 1.732                                | 1.559                                | 0.693                                 | 0.087                                | 0.078                                | 0.035                                 |
| TBJD337*006L□#@0^++            | D | 330   | 6                             | 0.045                        | 19.8          | 198           | 396            | 8            | 10           | 12            | 0.150                             | 1.826                                | 1.643                                | 0.730                                 | 0.082                                | 0.074                                | 0.033                                 |
| TBJE337*006C□#@0^++            | E | 330   | 6                             | 0.9                          | 19.8          | 198           | 396            | 8            | 10           | 12            | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE337*006L□#@0^++            | E | 330   | 6                             | 0.1                          | 19.8          | 198           | 396            | 8            | 10           | 12            | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJV337*006L□#@0^++            | V | 330   | 6                             | 0.1                          | 19.8          | 198           | 396            | 8            | 10           | 12            | 0.250                             | 1.581                                | 1.423                                | 0.632                                 | 0.158                                | 0.142                                | 0.063                                 |
| TBJD477*006C□#@0^++            | D | 470   | 6                             | 0.06                         | 28.2          | 282           | 564            | 12           | 14           | 16            | 0.150                             | 1.581                                | 1.423                                | 0.632                                 | 0.095                                | 0.085                                | 0.038                                 |
| TBJD477*006L□#@0^++            | D | 470   | 6                             | 0.045                        | 28.2          | 282           | 564            | 12           | 14           | 16            | 0.150                             | 1.826                                | 1.643                                | 0.730                                 | 0.082                                | 0.074                                | 0.033                                 |
| TBJE477*006C□#@0^++            | E | 470   | 6                             | 0.9                          | 28.2          | 282           | 564            | 10           | 12           | 14            | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE477*006L□#@0^++            | E | 470   | 6                             | 0.05                         | 28.2          | 282           | 564            | 10           | 12           | 14            | 0.165                             | 1.817                                | 1.635                                | 0.727                                 | 0.091                                | 0.082                                | 0.036                                 |
| TBJV477*006C□#@0^++            | V | 470   | 6                             | 0.1                          | 28.2          | 282           | 564            | 10           | 12           | 14            | 0.250                             | 1.581                                | 1.423                                | 0.632                                 | 0.158                                | 0.142                                | 0.063                                 |
| TBJV477*006L□#@0^++            | V | 470   | 6                             | 0.055                        | 28.2          | 282           | 564            | 10           | 12           | 14            | 0.250                             | 2.132                                | 1.919                                | 0.853                                 | 0.117                                | 0.106                                | 0.047                                 |
| TBJE687*006C□#@0^++            | E | 680   | 6                             | 0.06                         | 40.8          | 408           | 816            | 10           | 12           | 14            | 0.165                             | 1.658                                | 1.492                                | 0.663                                 | 0.099                                | 0.090                                | 0.040                                 |
| TBJE687*006L□#@0^++            | E | 680   | 6                             | 0.045                        | 40.8          | 408           | 816            | 10           | 12           | 14            | 0.165                             | 1.915                                | 1.723                                | 0.766                                 | 0.086                                | 0.078                                | 0.034                                 |
| TBJV687*006C□#@0^++            | V | 680   | 6                             | 0.04                         | 40.8          | 408           | 816            | 10           | 12           | 14            | 0.250                             | 2.500                                | 2.250                                | 1.000                                 | 0.100                                | 0.090                                | 0.040                                 |
| TBJV687*006L□#@0^++            | V | 680   | 6                             | 0.035                        | 40.8          | 408           | 816            | 14           | 17           | 20            | 0.250                             | 2.673                                | 2.405                                | 1.069                                 | 0.094                                | 0.084                                | 0.037                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                                 |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|---------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR<br>@ 100kHz<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |                  |              | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                                 | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJV108*006C□#@0^++            | V | 1000  | 6                             | 0.05                            | 60            | 600           | 1200           | 16           | 19               | 21           | 0.250                             | 2.236                                | 2.012                                | 0.894                                 | 0.112                                | 0.101                                | 0.045                                 |
| TBJV108*006L□#@0^++            | V | 1000  | 6                             | 0.04                            | 60            | 600           | 1200           | 16           | 19               | 21           | 0.250                             | 2.500                                | 2.250                                | 1.000                                 | 0.100                                | 0.090                                | 0.040                                 |
| TBJA105*010C□#@0^++            | A | 1   | 10                            | 10                              | 0.1           | 1             | 1.2            | 4            | 6                | 6            | 0.075                             | 0.087                                | 0.078                                | 0.035                                 | 0.866                                | 0.779                                | 0.346                                 |
| TBJA155*010C□#@0^++            | A | 1.5   | 10                            | 8                               | 0.15          | 1.5           | 1.8            | 6            | 6                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJA225*010C□#@0^++            | A | 2.2   | 10                            | 8                               | 0.22          | 2.2           | 2.64           | 6            | 9                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJA225*010L□#@0^++            | A | 2.2   | 10                            | 1.8                             | 0.22          | 2.2           | 4.4            | 6            | 9                | 10           | 0.075                             | 0.204                                | 0.184                                | 0.082                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJB335*010C□#@0^++            | B | 3.3   | 10                            | 5.5                             | 0.33          | 3.3           | 3.96           | 6            | 9                | 9            | 0.085                             | 0.124                                | 0.112                                | 0.050                                 | 0.684                                | 0.615                                | 0.273                                 |
| TBJA475*010C□#@0^++            | A | 4.7   | 10                            | 5                               | 0.47          | 4.7           | 9.4            | 6            | 9                | 10           | 0.075                             | 0.122                                | 0.110                                | 0.049                                 | 0.612                                | 0.551                                | 0.245                                 |
| TBJA475*010L□#@0^++            | A | 4.7   | 10                            | 1.4                             | 0.47          | 4.7           | 9.4            | 6            | 9                | 10           | 0.075                             | 0.231                                | 0.208                                | 0.093                                 | 0.324                                | 0.292                                | 0.130                                 |
| TBJB475*010C□#@0^++            | B | 4.7   | 10                            | 4.5                             | 0.47          | 4.7           | 5.64           | 6            | 9                | 9            | 0.085                             | 0.137                                | 0.124                                | 0.055                                 | 0.618                                | 0.557                                | 0.247                                 |
| TBJA685*010C□#@0^++            | A | 6.8   | 10                            | 4                               | 0.68          | 6.8           | 13.6           | 6            | 9                | 10           | 0.075                             | 0.137                                | 0.123                                | 0.055                                 | 0.548                                | 0.493                                | 0.219                                 |
| TBJA685*010L□#@0^++            | A | 6.8   | 10                            | 1.8                             | 0.68          | 6.8           | 13.6           | 6            | 9                | 10           | 0.075                             | 0.204                                | 0.184                                | 0.082                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJB685*010C□#@0^++            | B | 6.8   | 10                            | 3.5                             | 0.68          | 6.8           | 8.16           | 6            | 9                | 9            | 0.085                             | 0.156                                | 0.140                                | 0.062                                 | 0.545                                | 0.491                                | 0.218                                 |
| TBJA106*010C□#@0^++            | A | 10  | 10                            | 3                               | 1             | 10            | 20             | 6            | 9                | 10           | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJA106*010L□#@0^++            | A | 10  | 10                            | 1.8                             | 1             | 10            | 20             | 6            | 9                | 10           | 0.075                             | 0.204                                | 0.184                                | 0.082                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJB106*010C□#@0^++            | B | 10  | 10                            | 2.5                             | 1             | 10            | 20             | 6            | 9                | 10           | 0.085                             | 0.184                                | 0.166                                | 0.074                                 | 0.461                                | 0.415                                | 0.184                                 |
| TBJA156*010C□#@0^++            | A | 15  | 10                            | 3.2                             | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.075                             | 0.153                                | 0.138                                | 0.061                                 | 0.490                                | 0.441                                | 0.196                                 |
| TBJA156*010L□#@0^++            | A | 15  | 10                            | 1                               | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.075                             | 0.274                                | 0.246                                | 0.110                                 | 0.274                                | 0.246                                | 0.110                                 |
| TBJB156*010C□#@0^++            | B | 15  | 10                            | 2.8                             | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.085                             | 0.174                                | 0.157                                | 0.070                                 | 0.488                                | 0.439                                | 0.195                                 |
| TBJB156*010L□#@0^++            | B | 15  | 10                            | 0.45                            | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.085                             | 0.435                                | 0.391                                | 0.174                                 | 0.196                                | 0.176                                | 0.078                                 |
| TBJC156*010C□#@0^++            | C | 15  | 10                            | 2.5                             | 1.5           | 15            | 18             | 6            | 9                | 10           | 0.110                             | 0.210                                | 0.189                                | 0.084                                 | 0.524                                | 0.472                                | 0.210                                 |
| TBJB226*010C□#@0^++            | B | 22  | 10                            | 2.4                             | 2.2           | 22            | 44             | 6            | 9                | 10           | 0.085                             | 0.188                                | 0.169                                | 0.075                                 | 0.452                                | 0.406                                | 0.181                                 |
| TBJB226*010L□#@0^++            | B | 22  | 10                            | 0.7                             | 2.2           | 22            | 44             | 6            | 9                | 10           | 0.085                             | 0.348                                | 0.314                                | 0.139                                 | 0.244                                | 0.220                                | 0.098                                 |
| TBJC226*010C□#@0^++            | C | 22  | 10                            | 1                               | 2.2           | 22            | 44             | 6            | 9                | 10           | 0.110                             | 0.332                                | 0.298                                | 0.133                                 | 0.332                                | 0.298                                | 0.133                                 |
| TBJC226*010L□#@0^++            | C | 22  | 10                            | 0.3                             | 2.2           | 22            | 44             | 6            | 9                | 10           | 0.110                             | 0.606                                | 0.545                                | 0.242                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJA336*010C□#@0^++            | A | 33  | 10                            | 1.7                             | 3.3           | 33            | 66             | 8            | 10               | 12           | 0.075                             | 0.210                                | 0.189                                | 0.084                                 | 0.357                                | 0.321                                | 0.143                                 |
| TBJA336*010L□#@0^++            | A | 33  | 10                            | 0.7                             | 3.3           | 33            | 66             | 8            | 10               | 12           | 0.075                             | 0.327                                | 0.295                                | 0.131                                 | 0.229                                | 0.206                                | 0.092                                 |
| TBJB336*010C□#@0^++            | B | 33  | 10                            | 1.8                             | 3.3           | 33            | 66             | 6            | 9                | 10           | 0.085                             | 0.217                                | 0.196                                | 0.087                                 | 0.391                                | 0.352                                | 0.156                                 |
| TBJB336*010L□#@0^++            | B | 33  | 10                            | 0.25                            | 3.3           | 33            | 66             | 6            | 8                | 10           | 0.085                             | 0.583                                | 0.525                                | 0.233                                 | 0.146                                | 0.131                                | 0.058                                 |
| TBJC336*010C□#@0^++            | C | 33  | 10                            | 1.6                             | 3.3           | 33            | 66             | 6            | 9                | 10           | 0.110                             | 0.262                                | 0.236                                | 0.105                                 | 0.420                                | 0.378                                | 0.168                                 |
| TBJC336*010L□#@0^++            | C | 33  | 10                            | 0.15                            | 3.3           | 33            | 66             | 6            | 9                | 10           | 0.110                             | 0.856                                | 0.771                                | 0.343                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD336*010C□#@0^++            | D | 33  | 10                            | 1.1                             | 3.3           | 33            | 39.6           | 6            | 9                | 9            | 0.150                             | 0.369                                | 0.332                                | 0.148                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJB476*010C□#@0^++            | B | 47  | 10                            | 0.35                            | 4.7           | 47            | 94             | 8            | 10               | 12           | 0.085                             | 0.493                                | 0.444                                | 0.197                                 | 0.172                                | 0.155                                | 0.069                                 |
| TBJB476*010L□#@0^++            | B | 47  | 10                            | 0.25                            | 4.7           | 47            | 94             | 8            | 10               | 12           | 0.085                             | 0.583                                | 0.525                                | 0.233                                 | 0.146                                | 0.131                                | 0.058                                 |
| TBJC476*010C□#@0^++            | C | 47  | 10                            | 1.2                             | 4.7           | 47            | 94             | 6            | 9                | 10           | 0.110                             | 0.303                                | 0.272                                | 0.121                                 | 0.363                                | 0.327                                | 0.145                                 |
| TBJC476*010L□#@0^++            | C | 47  | 10                            | 0.2                             | 4.7           | 47            | 94             | 6            | 9                | 10           | 0.110                             | 0.742                                | 0.667                                | 0.297                                 | 0.148                                | 0.133                                | 0.059                                 |
| TBJD476*010C□#@0^++            | D | 47  | 10                            | 0.9                             | 4.7           | 47            | 56.4           | 6            | 9                | 9            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD476*010L□#@0^++            | D | 47  | 10                            | 0.1                             | 4.7           | 47            | 94             | 6            | 9                | 10           | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJB686*010L□#@0^++            | B | 68  | 10                            | 0.6                             | 6.8           | 68            | 136            | 8            | 10               | 12           | 0.085                             | 0.376                                | 0.339                                | 0.151                                 | 0.226                                | 0.203                                | 0.090                                 |
| TBJC686*010C□#@0^++            | C | 68  | 10                            | 1.2                             | 6.8           | 68            | 136            | 6            | 10               | 12           | 0.110                             | 0.303                                | 0.272                                | 0.121                                 | 0.363                                | 0.327                                | 0.145                                 |
| TBJC686*010L□#@0^++            | C | 68  | 10                            | 0.08                            | 6.8           | 68            | 136            | 6            | 10               | 12           | 0.110                             | 1.173                                | 1.055                                | 0.469                                 | 0.094                                | 0.084                                | 0.038                                 |
| TBJD686*010C□#@0^++            | D | 68  | 10                            | 0.9                             | 6.8           | 68            | 136            | 6            | 9                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD686*010L□#@0^++            | D | 68  | 10                            | 0.1                             | 6.8           | 68            | 136            | 6            | 9                | 10           | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJB107*010L□#@0^++            | B | 100   | 10                            | 0.4                             | 10            | 100           | 200            | 8            | 10               | 12           | 0.085                             | 0.461                                | 0.415                                | 0.184                                 | 0.184                                | 0.166                                | 0.074                                 |
| TBJC107*010C□#@0^++            | C | 100   | 10                            | 1.2                             | 10            | 100           | 200            | 8            | 10               | 12           | 0.110                             | 0.303                                | 0.272                                | 0.121                                 | 0.363                                | 0.327                                | 0.145                                 |
| TBJC107*010L□#@0^++            | C | 100   | 10                            | 0.2                             | 10            | 100           | 200            | 8            | 10               | 12           | 0.110                             | 0.742                                | 0.667                                | 0.297                                 | 0.148                                | 0.133                                | 0.059                                 |
| TBJD107*010C□#@0^++            | D | 100   | 10                            | 0.9                             | 10            | 100           | 200            | 6            | 9                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD107*010L□#@0^++            | D | 100   | 10                            | 0.1                             | 10            | 100           | 200            | 6            | 9                | 10           | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJE107*010C□#@0^++            | E | 100   | 10                            | 0.125                           | 10            | 100           | 200            | 6            | 9                | 10           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD157*010C□#@0^++            | D | 150   | 10                            | 0.9                             | 15            | 150           | 300            | 8            | 10               | 12           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD157*010L□#@0^++            | D | 150   | 10                            | 0.1                             | 15            | 150           | 300            | 8            | 10               | 12           | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJE157*010C□#@0^++            | E | 150   | 10                            | 0.1                             | 15            | 150           | 300            | 8            | 10               | 12           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD227*010C□#@0^++            | D | 220   | 10                            | 0.9                             | 22            | 220           | 440            | 8            | 10               | 12           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD227*010L□#@0^++            | D | 220   | 10                            | 0.15                            | 22            | 220           | 440            | 8            | 10               | 12           | 0.150                             | 1.000                                | 0.900                                | 0.400                                 | 0.150                                | 0.135                                | 0.060                                 |
| TBJE227*010C□#@0^++            | E | 220   | 10                            | 0.9                             | 22            | 220           | 440            | 8            | 10               | 12           | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE227*010L□#@0^++            | E | 220   | 10                            | 0.1                             | 22            | 220           | 440            | 8            | 10               | 12           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                     |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|---------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |                  |              | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                     | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJD337*010L□#@0^++            | D | 330   | 10                            | 0.15                | 33            | 330           | 660            | 8            | 10               | 12           | 0.150                             | 1.000                                | 0.900                                | 0.400                                 | 0.150                                | 0.135                                | 0.060                                 |
| TBJE337*010C□#@0^++            | E | 330   | 10                            | 0.9                 | 33            | 330           | 660            | 8            | 10               | 12           | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE337*010L□#@0^++            | E | 330   | 10                            | 0.06                | 33            | 330           | 660            | 8            | 10               | 12           | 0.165                             | 1.658                                | 1.492                                | 0.663                                 | 0.099                                | 0.090                                | 0.040                                 |
| TBJV337*010C□#@0^++            | V | 330   | 10                            | 0.1                 | 33            | 330           | 660            | 8            | 10               | 12           | 0.250                             | 1.581                                | 1.423                                | 0.632                                 | 0.158                                | 0.142                                | 0.063                                 |
| TBJV337*010L□#@0^++            | V | 330   | 10                            | 0.06                | 33            | 330           | 660            | 10           | 10               | 12           | 0.250                             | 2.041                                | 1.837                                | 0.816                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJE477*010C□#@0^++            | E | 470   | 10                            | 0.9                 | 47            | 470           | 940            | 10           | 12               | 14           | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE477*010L□#@0^++            | E | 470   | 10                            | 0.05                | 47            | 470           | 940            | 10           | 12               | 14           | 0.165                             | 1.817                                | 1.635                                | 0.727                                 | 0.091                                | 0.082                                | 0.036                                 |
| TBJV477*010C□#@0^++            | V | 470   | 10                            | 0.1                 | 47            | 470           | 940            | 10           | 12               | 14           | 0.250                             | 1.581                                | 1.423                                | 0.632                                 | 0.158                                | 0.142                                | 0.063                                 |
| TBJV477*010L□#@0^++            | V | 470   | 10                            | 0.06                | 47            | 470           | 940            | 10           | 12               | 14           | 0.250                             | 2.041                                | 1.837                                | 0.816                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJA684*015C□#@0^++            | A | 0.68  | 15                            | 12                  | 0.102         | 1.02          | 1.224          | 4            | 6                | 6            | 0.075                             | 0.079                                | 0.071                                | 0.032                                 | 0.949                                | 0.854                                | 0.379                                 |
| TBJA105*015C□#@0^++            | A | 1   | 15                            | 10                  | 0.15          | 1.5           | 1.8            | 4            | 6                | 6            | 0.075                             | 0.087                                | 0.078                                | 0.035                                 | 0.866                                | 0.779                                | 0.346                                 |
| TBJA155*015C□#@0^++            | A | 1.5   | 15                            | 8                   | 0.225         | 2.25          | 2.7            | 6            | 9                | 9            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJB225*015C□#@0^++            | B | 2.2   | 15                            | 5.5                 | 0.33          | 3.3           | 3.96           | 6            | 9                | 9            | 0.085                             | 0.124                                | 0.112                                | 0.050                                 | 0.684                                | 0.615                                | 0.273                                 |
| TBJB335*015C□#@0^++            | B | 3.3   | 15                            | 5                   | 0.495         | 4.95          | 5.94           | 6            | 8                | 9            | 0.085                             | 0.130                                | 0.117                                | 0.052                                 | 0.652                                | 0.587                                | 0.261                                 |
| TBJB475*015C□#@0^++            | B | 4.7   | 15                            | 4                   | 0.705         | 7.05          | 8.46           | 6            | 8                | 8            | 0.085                             | 0.146                                | 0.131                                | 0.058                                 | 0.583                                | 0.525                                | 0.233                                 |
| TBJC106*015C□#@0^++            | C | 10  | 15                            | 2.5                 | 1.5           | 15            | 18             | 6            | 8                | 9            | 0.110                             | 0.210                                | 0.189                                | 0.084                                 | 0.524                                | 0.472                                | 0.210                                 |
| TBJD226*015C□#@0^++            | D | 22  | 15                            | 1.1                 | 3.3           | 33            | 39.6           | 6            | 8                | 9            | 0.150                             | 0.369                                | 0.332                                | 0.148                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJD336*015C□#@0^++            | D | 33  | 15                            | 0.9                 | 4.95          | 49.5          | 59.4           | 6            | 8                | 9            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD157*015L□#@0^++            | D | 150   | 15                            | 0.05                | 5.625         | 56.25         | 112.5          | 6            | 9                | 10           | 0.150                             | 1.732                                | 1.559                                | 0.693                                 | 0.087                                | 0.078                                | 0.035                                 |
| TBJA684*016C□#@0^++            | A | 0.68  | 16                            | 12                  | 0.109         | 1.088         | 2.176          | 4            | 6                | 6            | 0.075                             | 0.079                                | 0.071                                | 0.032                                 | 0.949                                | 0.854                                | 0.379                                 |
| TBJA105*016C□#@0^++            | A | 1   | 16                            | 10                  | 0.16          | 1.6           | 3.2            | 4            | 6                | 6            | 0.075                             | 0.087                                | 0.078                                | 0.035                                 | 0.866                                | 0.779                                | 0.346                                 |
| TBJA225*016C□#@0^++            | A | 2.2   | 16                            | 5.5                 | 0.352         | 3.52          | 7.04           | 6            | 9                | 10           | 0.075                             | 0.117                                | 0.105                                | 0.047                                 | 0.642                                | 0.578                                | 0.257                                 |
| TBJA225*016L□#@0^++            | A | 2.2   | 16                            | 1.8                 | 0.352         | 3.52          | 7.04           | 6            | 9                | 10           | 0.075                             | 0.204                                | 0.184                                | 0.082                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJB225*016C□#@0^++            | B | 2.2   | 16                            | 5                   | 0.352         | 3.52          | 7.04           | 6            | 8                | 8            | 0.085                             | 0.130                                | 0.117                                | 0.052                                 | 0.652                                | 0.587                                | 0.261                                 |
| TBJA335*016C□#@0^++            | A | 3.3   | 16                            | 5                   | 0.528         | 5.28          | 10.56          | 6            | 9                | 10           | 0.075                             | 0.122                                | 0.110                                | 0.049                                 | 0.612                                | 0.551                                | 0.245                                 |
| TBJA335*016L□#@0^++            | A | 3.3   | 16                            | 3.5                 | 0.528         | 5.28          | 10.56          | 6            | 9                | 10           | 0.075                             | 0.146                                | 0.132                                | 0.059                                 | 0.512                                | 0.461                                | 0.205                                 |
| TBJB335*016C□#@0^++            | B | 3.3   | 16                            | 4.5                 | 0.528         | 5.28          | 10.56          | 6            | 9                | 10           | 0.085                             | 0.137                                | 0.124                                | 0.055                                 | 0.618                                | 0.557                                | 0.247                                 |
| TBJA475*016C□#@0^++            | A | 4.7   | 16                            | 4                   | 0.752         | 7.52          | 15.04          | 6            | 9                | 10           | 0.075                             | 0.137                                | 0.123                                | 0.055                                 | 0.548                                | 0.493                                | 0.219                                 |
| TBJA475*016L□#@0^++            | A | 4.7   | 16                            | 2                   | 0.752         | 7.52          | 15.04          | 6            | 9                | 10           | 0.075                             | 0.194                                | 0.174                                | 0.077                                 | 0.387                                | 0.349                                | 0.155                                 |
| TBJB475*016C□#@0^++            | B | 4.7   | 16                            | 3.1                 | 0.752         | 7.52          | 15.04          | 6            | 8                | 8            | 0.085                             | 0.166                                | 0.149                                | 0.066                                 | 0.513                                | 0.462                                | 0.205                                 |
| TBJB475*016L□#@0^++            | B | 4.7   | 16                            | 0.8                 | 0.752         | 7.52          | 15.04          | 6            | 9                | 10           | 0.085                             | 0.326                                | 0.293                                | 0.130                                 | 0.261                                | 0.235                                | 0.104                                 |
| TBJA685*016C□#@0^++            | A | 6.8   | 16                            | 2.5                 | 1.088         | 10.88         | 21.76          | 6            | 9                | 10           | 0.075                             | 0.173                                | 0.156                                | 0.069                                 | 0.433                                | 0.390                                | 0.173                                 |
| TBJA685*016L□#@0^++            | A | 6.8   | 16                            | 1.5                 | 1.088         | 10.88         | 21.76          | 6            | 9                | 10           | 0.075                             | 0.224                                | 0.201                                | 0.089                                 | 0.335                                | 0.302                                | 0.134                                 |
| TBJB685*016C□#@0^++            | B | 6.8   | 16                            | 2.5                 | 1.088         | 10.88         | 21.76          | 6            | 9                | 10           | 0.085                             | 0.184                                | 0.166                                | 0.074                                 | 0.461                                | 0.415                                | 0.184                                 |
| TBJB685*016L□#@0^++            | B | 6.8   | 16                            | 0.6                 | 1.088         | 10.88         | 21.76          | 6            | 9                | 10           | 0.085                             | 0.376                                | 0.339                                | 0.151                                 | 0.226                                | 0.203                                | 0.090                                 |
| TBJA106*016C□#@0^++            | A | 10  | 16                            | 3                   | 1.6           | 16            | 32             | 8            | 10               | 12           | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJA106*016L□#@0^++            | A | 10  | 16                            | 1                   | 1.6           | 16            | 32             | 8            | 10               | 12           | 0.075                             | 0.274                                | 0.246                                | 0.110                                 | 0.274                                | 0.246                                | 0.110                                 |
| TBJB106*016C□#@0^++            | B | 10  | 16                            | 2.8                 | 1.6           | 16            | 32             | 6            | 9                | 10           | 0.085                             | 0.174                                | 0.157                                | 0.070                                 | 0.488                                | 0.439                                | 0.195                                 |
| TBJB106*016L□#@0^++            | B | 10  | 16                            | 0.5                 | 1.6           | 16            | 32             | 6            | 9                | 10           | 0.085                             | 0.412                                | 0.371                                | 0.165                                 | 0.206                                | 0.186                                | 0.082                                 |
| TBJC106*016C□#@0^++            | C | 10  | 16                            | 2.5                 | 1.6           | 16            | 32             | 6            | 8                | 10           | 0.110                             | 0.210                                | 0.189                                | 0.084                                 | 0.524                                | 0.472                                | 0.210                                 |
| TBJC106*016L□#@0^++            | C | 10  | 16                            | 0.5                 | 1.6           | 16            | 32             | 6            | 9                | 10           | 0.110                             | 0.469                                | 0.422                                | 0.188                                 | 0.235                                | 0.211                                | 0.094                                 |
| TBJB156*016C□#@0^++            | B | 15  | 16                            | 2.5                 | 2.4           | 24            | 48             | 6            | 9                | 10           | 0.085                             | 0.184                                | 0.166                                | 0.074                                 | 0.461                                | 0.415                                | 0.184                                 |
| TBJB156*016L□#@0^++            | B | 15  | 16                            | 0.8                 | 2.4           | 24            | 48             | 6            | 9                | 10           | 0.085                             | 0.326                                | 0.293                                | 0.130                                 | 0.261                                | 0.235                                | 0.104                                 |
| TBJC156*016C□#@0^++            | C | 15  | 16                            | 1.8                 | 2.4           | 24            | 48             | 6            | 9                | 10           | 0.110                             | 0.247                                | 0.222                                | 0.099                                 | 0.445                                | 0.400                                | 0.178                                 |
| TBJB226*016C□#@0^++            | B | 22  | 16                            | 2.3                 | 3.52          | 35.2          | 70.4           | 6            | 9                | 10           | 0.085                             | 0.192                                | 0.173                                | 0.077                                 | 0.442                                | 0.398                                | 0.177                                 |
| TBJB226*016L□#@0^++            | B | 22  | 16                            | 0.6                 | 3.52          | 35.2          | 70.4           | 6            | 9                | 10           | 0.085                             | 0.376                                | 0.339                                | 0.151                                 | 0.226                                | 0.203                                | 0.090                                 |
| TBJC226*016C□#@0^++            | C | 22  | 16                            | 1.6                 | 3.52          | 35.2          | 70.4           | 6            | 9                | 10           | 0.110                             | 0.262                                | 0.236                                | 0.105                                 | 0.420                                | 0.378                                | 0.168                                 |
| TBJC226*016L□#@0^++            | C | 22  | 16                            | 0.375               | 3.52          | 35.2          | 70.4           | 6            | 9                | 10           | 0.110                             | 0.542                                | 0.487                                | 0.217                                 | 0.203                                | 0.183                                | 0.081                                 |
| TBJD226*016C□#@0^++            | D | 22  | 16                            | 1.1                 | 3.52          | 35.2          | 70.4           | 6            | 8                | 9            | 0.150                             | 0.369                                | 0.332                                | 0.148                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJB336*016L□#@0^++            | B | 33  | 16                            | 0.35                | 5.28          | 52.8          | 105.6          | 8            | 10               | 12           | 0.085                             | 0.493                                | 0.444                                | 0.197                                 | 0.172                                | 0.155                                | 0.069                                 |
| TBJC336*016C□#@0^++            | C | 33  | 16                            | 1.5                 | 5.28          | 52.8          | 105.6          | 6            | 9                | 10           | 0.110                             | 0.271                                | 0.244                                | 0.108                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJC336*016L□#@0^++            | C | 33  | 16                            | 0.3                 | 5.28          | 52.8          | 105.6          | 6            | 9                | 10           | 0.110                             | 0.606                                | 0.545                                | 0.242                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJD336*016C□#@0^++            | D | 33  | 16                            | 0.9                 | 5.28          | 52.8          | 105.6          | 6            | 9                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD336*016L□#@0^++            | D | 33  | 16                            | 0.2                 | 5.28          | 52.8          | 105.6          | 6            | 9                | 10           | 0.150                             | 0.866                                | 0.779                                | 0.346                                 | 0.173                                | 0.156                                | 0.069                                 |
| TBJC476*016C□#@0^++            | C | 47  | 16                            | 1.5                 | 7.52          | 75.2          | 150.4          | 6            | 9                | 10           | 0.110                             | 0.271                                | 0.244                                | 0.108                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJC476*016L□#@0^++            | C | 47  | 16                            | 0.35                | 7.52          | 75.2          | 150.4          | 6            | 9                | 10           | 0.110                             | 0.561                                | 0.505                                | 0.224                                 | 0.196                                | 0.177                                | 0.078                                 |
| TBJD476*016C□#@0^++            | D | 47  | 16                            | 0.9                 | 7.52          | 75.2          | 150.4          | 6            | 9                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD476*016L□#@0^++            | D | 47  | 16                            | 0.15                | 7.52          | 75.2          | 150.4          | 6            | 9                | 10           | 0.150                             | 1.000                                | 0.900                                | 0.400                                 | 0.150                                | 0.135                                | 0.060                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                              |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |                  |              | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                              | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJC686*016C□#@0^++            | C | 68  | 16                            | 0.2                          | 10.88         | 108.8         | 217.6          | 6            | 9                | 10           | 0.110                             | 0.742                                | 0.667                                | 0.297                                 | 0.148                                | 0.133                                | 0.059                                 |
| TBJC686*016L□#@0^++            | C | 68  | 16                            | 0.125                        | 10.88         | 108.8         | 217.6          | 6            | 9                | 10           | 0.110                             | 0.938                                | 0.844                                | 0.375                                 | 0.117                                | 0.106                                | 0.047                                 |
| TBJD686*016C□#@0^++            | D | 68  | 16                            | 0.9                          | 10.88         | 108.8         | 217.6          | 6            | 9                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD686*016L□#@0^++            | D | 68  | 16                            | 0.07                         | 10.88         | 108.8         | 217.6          | 6            | 9                | 10           | 0.150                             | 1.464                                | 1.317                                | 0.586                                 | 0.102                                | 0.092                                | 0.041                                 |
| TBJD107*016C□#@0^++            | D | 100   | 16                            | 0.9                          | 16            | 160           | 320            | 6            | 9                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD107*016L□#@0^++            | D | 100   | 16                            | 0.125                        | 16            | 160           | 320            | 6            | 9                | 10           | 0.150                             | 1.095                                | 0.986                                | 0.438                                 | 0.137                                | 0.123                                | 0.055                                 |
| TBJE107*016C□#@0^++            | E | 100   | 16                            | 0.9                          | 16            | 160           | 320            | 6            | 9                | 10           | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE107*016L□#@0^++            | E | 100   | 16                            | 0.1                          | 16            | 160           | 320            | 6            | 9                | 10           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD157*016C□#@0^++            | D | 150   | 16                            | 0.9                          | 24            | 240           | 480            | 6            | 9                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD157*016L□#@0^++            | D | 150   | 16                            | 0.15                         | 24            | 240           | 480            | 6            | 9                | 10           | 0.150                             | 1.000                                | 0.900                                | 0.400                                 | 0.150                                | 0.135                                | 0.060                                 |
| TBJE157*016C□#@0^++            | E | 150   | 16                            | 0.3                          | 24            | 240           | 480            | 6            | 9                | 10           | 0.165                             | 0.742                                | 0.667                                | 0.297                                 | 0.222                                | 0.200                                | 0.089                                 |
| TBJE157*016L□#@0^++            | E | 150   | 16                            | 0.1                          | 24            | 240           | 480            | 6            | 9                | 10           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJV157*016C□#@0^++            | V | 150   | 16                            | 0.075                        | 24            | 240           | 480            | 8            | 10               | 12           | 0.250                             | 1.826                                | 1.643                                | 0.730                                 | 0.137                                | 0.123                                | 0.055                                 |
| TBJV157*016L□#@0^++            | V | 150   | 16                            | 0.045                        | 24            | 240           | 480            | 6            | 8                | 10           | 0.250                             | 2.357                                | 2.121                                | 0.943                                 | 0.106                                | 0.095                                | 0.042                                 |
| TBJE227*016C□#@0^++            | E | 220   | 16                            | 0.15                         | 35.2          | 352           | 704            | 10           | 12               | 14           | 0.165                             | 1.049                                | 0.944                                | 0.420                                 | 0.157                                | 0.142                                | 0.063                                 |
| TBJE227*016L□#@0^++            | E | 220   | 16                            | 0.1                          | 35.2          | 352           | 704            | 10           | 12               | 14           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJV227*016C□#@0^++            | V | 220   | 16                            | 0.15                         | 35.2          | 352           | 704            | 8            | 10               | 12           | 0.250                             | 1.291                                | 1.162                                | 0.516                                 | 0.194                                | 0.174                                | 0.077                                 |
| TBJV227*016L□#@0^++            | V | 220   | 16                            | 0.075                        | 35.2          | 352           | 704            | 8            | 10               | 12           | 0.250                             | 1.826                                | 1.643                                | 0.730                                 | 0.137                                | 0.123                                | 0.055                                 |
| TBJA474*020C□#@0^++            | A | 0.47  | 20                            | 14                           | 0.5           | 5             | 10             | 4            | 6                | 6            | 0.075                             | 0.073                                | 0.066                                | 0.029                                 | 1.025                                | 0.922                                | 0.410                                 |
| TBJA684*020C□#@0^++            | A | 0.68  | 20                            | 12                           | 0.136         | 1.36          | 1.632          | 4            | 6                | 6            | 0.075                             | 0.079                                | 0.071                                | 0.032                                 | 0.949                                | 0.854                                | 0.379                                 |
| TBJA105*020C□#@0^++            | A | 1   | 20                            | 10                           | 0.2           | 2             | 2.4            | 4            | 6                | 6            | 0.075                             | 0.087                                | 0.078                                | 0.035                                 | 0.866                                | 0.779                                | 0.346                                 |
| TBJA105*020L□#@0^++            | A | 1   | 20                            | 3                            | 0.2           | 2             | 4              | 4            | 6                | 6            | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJA155*020C□#@0^++            | A | 1.5   | 20                            | 6.5                          | 0.3           | 3             | 6              | 4            | 8                | 10           | 0.075                             | 0.107                                | 0.097                                | 0.043                                 | 0.698                                | 0.628                                | 0.279                                 |
| TBJB155*020C□#@0^++            | B | 1.5   | 20                            | 6                            | 0.3           | 3             | 3.6            | 6            | 9                | 9            | 0.085                             | 0.119                                | 0.107                                | 0.048                                 | 0.714                                | 0.643                                | 0.286                                 |
| TBJA225*020C□#@0^++            | A | 2.2   | 20                            | 5.3                          | 0.44          | 4.4           | 8.8            | 6            | 8                | 8            | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJA225*020L□#@0^++            | A | 2.2   | 20                            | 3                            | 0.44          | 4.4           | 8.8            | 6            | 9                | 10           | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJB225*020C□#@0^++            | B | 2.2   | 20                            | 5                            | 0.44          | 4.4           | 5.28           | 6            | 8                | 9            | 0.085                             | 0.130                                | 0.117                                | 0.052                                 | 0.652                                | 0.587                                | 0.261                                 |
| TBJA335*020L□#@0^++            | A | 3.3   | 20                            | 2.5                          | 0.66          | 6.6           | 13.2           | 6            | 9                | 10           | 0.075                             | 0.173                                | 0.156                                | 0.069                                 | 0.433                                | 0.390                                | 0.173                                 |
| TBJB335*020C□#@0^++            | B | 3.3   | 20                            | 4                            | 0.66          | 6.6           | 7.92           | 6            | 9                | 9            | 0.085                             | 0.146                                | 0.131                                | 0.058                                 | 0.583                                | 0.525                                | 0.233                                 |
| TBJB335*020L□#@0^++            | B | 3.3   | 20                            | 1.3                          | 0.66          | 6.6           | 13.2           | 6            | 9                | 10           | 0.085                             | 0.256                                | 0.230                                | 0.102                                 | 0.332                                | 0.299                                | 0.133                                 |
| TBJA475*020C□#@0^++            | A | 4.7   | 20                            | 4                            | 0.94          | 9.4           | 18.8           | 6            | 8                | 10           | 0.075                             | 0.137                                | 0.123                                | 0.055                                 | 0.548                                | 0.493                                | 0.219                                 |
| TBJA475*020L□#@0^++            | A | 4.7   | 20                            | 1.8                          | 0.94          | 9.4           | 18.8           | 6            | 8                | 10           | 0.075                             | 0.204                                | 0.184                                | 0.082                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJB475*020C□#@0^++            | B | 4.7   | 20                            | 3                            | 0.94          | 9.4           | 18.8           | 6            | 8                | 10           | 0.085                             | 0.168                                | 0.151                                | 0.067                                 | 0.505                                | 0.454                                | 0.202                                 |
| TBJB475*020L□#@0^++            | B | 4.7   | 20                            | 0.75                         | 0.94          | 9.4           | 18.8           | 6            | 9                | 10           | 0.085                             | 0.337                                | 0.303                                | 0.135                                 | 0.252                                | 0.227                                | 0.101                                 |
| TBJC475*020C□#@0^++            | C | 4.7   | 20                            | 3                            | 0.94          | 9.4           | 11.28          | 6            | 8                | 9            | 0.110                             | 0.191                                | 0.172                                | 0.077                                 | 0.574                                | 0.517                                | 0.230                                 |
| TBJA685*020L□#@0^++            | A | 6.8   | 20                            | 1                            | 1.36          | 13.6          | 27.2           | 6            | 9                | 10           | 0.075                             | 0.274                                | 0.246                                | 0.110                                 | 0.274                                | 0.246                                | 0.110                                 |
| TBJB685*020C□#@0^++            | B | 6.8   | 20                            | 2.5                          | 1.36          | 13.6          | 27.2           | 6            | 8                | 10           | 0.085                             | 0.184                                | 0.166                                | 0.074                                 | 0.461                                | 0.415                                | 0.184                                 |
| TBJB685*020L□#@0^++            | B | 6.8   | 20                            | 0.6                          | 1.36          | 13.6          | 27.2           | 6            | 9                | 10           | 0.085                             | 0.376                                | 0.339                                | 0.151                                 | 0.226                                | 0.203                                | 0.090                                 |
| TBJC685*020C□#@0^++            | C | 6.8   | 20                            | 2.4                          | 1.36          | 13.6          | 16.32          | 6            | 9                | 9            | 0.110                             | 0.214                                | 0.193                                | 0.086                                 | 0.514                                | 0.462                                | 0.206                                 |
| TBJC685*020L□#@0^++            | C | 6.8   | 20                            | 0.7                          | 1.36          | 13.6          | 27.2           | 6            | 9                | 10           | 0.110                             | 0.396                                | 0.357                                | 0.159                                 | 0.277                                | 0.250                                | 0.111                                 |
| TBJB106*020C□#@0^++            | B | 10  | 20                            | 2.1                          | 2             | 20            | 40             | 6            | 8                | 10           | 0.085                             | 0.201                                | 0.181                                | 0.080                                 | 0.422                                | 0.380                                | 0.169                                 |
| TBJB106*020L□#@0^++            | B | 10  | 20                            | 1                            | 2             | 20            | 40             | 6            | 8                | 10           | 0.085                             | 0.292                                | 0.262                                | 0.117                                 | 0.292                                | 0.262                                | 0.117                                 |
| TBJC106*020C□#@0^++            | C | 10  | 20                            | 1.9                          | 2             | 20            | 40             | 6            | 8                | 10           | 0.110                             | 0.241                                | 0.217                                | 0.096                                 | 0.457                                | 0.411                                | 0.183                                 |
| TBJC106*020L□#@0^++            | C | 10  | 20                            | 0.5                          | 2             | 20            | 40             | 6            | 9                | 10           | 0.110                             | 0.469                                | 0.422                                | 0.188                                 | 0.235                                | 0.211                                | 0.094                                 |
| TBJB156*020C□#@0^++            | B | 15  | 20                            | 2                            | 3             | 30            | 60             | 6            | 8                | 10           | 0.085                             | 0.206                                | 0.186                                | 0.082                                 | 0.412                                | 0.371                                | 0.165                                 |
| TBJB156*020L□#@0^++            | B | 15  | 20                            | 0.5                          | 3             | 30            | 60             | 6            | 9                | 10           | 0.085                             | 0.412                                | 0.371                                | 0.165                                 | 0.206                                | 0.186                                | 0.082                                 |
| TBJC156*020C□#@0^++            | C | 15  | 20                            | 1.7                          | 3             | 30            | 60             | 6            | 8                | 10           | 0.110                             | 0.254                                | 0.229                                | 0.102                                 | 0.432                                | 0.389                                | 0.173                                 |
| TBJC156*020L□#@0^++            | C | 15  | 20                            | 0.4                          | 3             | 30            | 60             | 6            | 8                | 10           | 0.110                             | 0.524                                | 0.472                                | 0.210                                 | 0.210                                | 0.189                                | 0.084                                 |
| TBJD156*020C□#@0^++            | D | 15  | 20                            | 1.1                          | 3             | 30            | 36             | 6            | 8                | 9            | 0.150                             | 0.369                                | 0.332                                | 0.148                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJB226*020C□#@0^++            | B | 22  | 20                            | 0.6                          | 4.4           | 44            | 88             | 6            | 9                | 10           | 0.085                             | 0.376                                | 0.339                                | 0.151                                 | 0.226                                | 0.203                                | 0.090                                 |
| TBJB226*020L□#@0^++            | B | 22  | 20                            | 0.4                          | 4.4           | 44            | 88             | 6            | 9                | 10           | 0.085                             | 0.461                                | 0.415                                | 0.184                                 | 0.184                                | 0.166                                | 0.074                                 |
| TBJC226*020C□#@0^++            | C | 22  | 20                            | 1.6                          | 4.4           | 44            | 88             | 6            | 8                | 10           | 0.110                             | 0.262                                | 0.236                                | 0.105                                 | 0.420                                | 0.378                                | 0.168                                 |
| TBJC226*020L□#@0^++            | C | 22  | 20                            | 0.15                         | 4.4           | 44            | 88             | 6            | 8                | 10           | 0.110                             | 0.856                                | 0.771                                | 0.343                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJD226*020C□#@0^++            | D | 22  | 20                            | 0.9                          | 4.4           | 44            | 52.8           | 6            | 9                | 9            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD226*020L□#@0^++            | D | 22  | 20                            | 0.2                          | 4.4           | 44            | 88             | 6            | 9                | 10           | 0.150                             | 0.866                                | 0.779                                | 0.346                                 | 0.173                                | 0.156                                | 0.069                                 |
| TBJC336*020C□#@0^++            | C | 33  | 20                            | 1.5                          | 6.6           | 66            | 132            | 6            | 8                | 10           | 0.110                             | 0.271                                | 0.244                                | 0.108                                 | 0.406                                | 0.366                                | 0.162                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                     |               |               |                |              |              |               | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|---------------------|---------------|---------------|----------------|--------------|--------------|---------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |              |               | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                     | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85°C<br>(%) | +125°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJC336*020L□#@0^++            | C | 33  | 20                            | 0.3                 | 6.6           | 66            | 132            | 6            | 9            | 10            | 0.110                             | 0.606                                | 0.545                                | 0.242                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJD336*020C□#@0^++            | D | 33  | 20                            | 0.9                 | 6.6           | 66            | 132            | 6            | 8            | 10            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD336*020L□#@0^++            | D | 33  | 20                            | 0.1                 | 6.6           | 66            | 132            | 6            | 8            | 10            | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJD476*020C□#@0^++            | D | 47  | 20                            | 0.2                 | 9.4           | 94            | 188            | 6            | 8            | 10            | 0.150                             | 0.866                                | 0.779                                | 0.346                                 | 0.173                                | 0.156                                | 0.069                                 |
| TBJD476*020L□#@0^++            | D | 47  | 20                            | 0.1                 | 9.4           | 94            | 188            | 6            | 8            | 10            | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJE476*020C□#@0^++            | E | 47  | 20                            | 0.25                | 9.4           | 94            | 188            | 6            | 8            | 8             | 0.165                             | 0.812                                | 0.731                                | 0.325                                 | 0.203                                | 0.183                                | 0.081                                 |
| TBJE476*020L□#@0^++            | E | 47  | 20                            | 0.07                | 9.4           | 94            | 188            | 6            | 9            | 10            | 0.165                             | 1.535                                | 1.382                                | 0.614                                 | 0.107                                | 0.097                                | 0.043                                 |
| TBJD686*020C□#@0^++            | D | 68  | 20                            | 0.9                 | 13.6          | 136           | 272            | 6            | 8            | 10            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD686*020L□#@0^++            | D | 68  | 20                            | 0.07                | 13.6          | 136           | 272            | 6            | 9            | 10            | 0.150                             | 1.464                                | 1.317                                | 0.586                                 | 0.102                                | 0.092                                | 0.041                                 |
| TBJE686*020C□#@0^++            | E | 68  | 20                            | 0.9                 | 13.6          | 136           | 272            | 6            | 8            | 10            | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE686*020L□#@0^++            | E | 68  | 20                            | 0.15                | 13.6          | 136           | 272            | 6            | 8            | 10            | 0.165                             | 1.049                                | 0.944                                | 0.420                                 | 0.157                                | 0.142                                | 0.063                                 |
| TBJD107*020C□#@0^++            | D | 100   | 20                            | 0.1                 | 20            | 200           | 400            | 6            | 9            | 10            | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJD107*020L□#@0^++            | D | 100   | 20                            | 0.085               | 20            | 200           | 400            | 6            | 9            | 10            | 0.150                             | 1.328                                | 1.196                                | 0.531                                 | 0.113                                | 0.102                                | 0.045                                 |
| TBJE107*020C□#@0^++            | E | 100   | 20                            | 0.15                | 20            | 200           | 400            | 6            | 9            | 10            | 0.165                             | 1.049                                | 0.944                                | 0.420                                 | 0.157                                | 0.142                                | 0.063                                 |
| TBJE107*020L□#@0^++            | E | 100   | 20                            | 0.1                 | 20            | 200           | 400            | 6            | 9            | 10            | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJV107*020C□#@0^++            | V | 100   | 20                            | 0.2                 | 20            | 200           | 400            | 8            | 10           | 12            | 0.250                             | 1.118                                | 1.006                                | 0.447                                 | 0.224                                | 0.201                                | 0.089                                 |
| TBJV107*020L□#@0^++            | V | 100   | 20                            | 0.085               | 20            | 200           | 400            | 8            | 10           | 12            | 0.250                             | 1.715                                | 1.543                                | 0.686                                 | 0.146                                | 0.131                                | 0.058                                 |
| TBJE157*020C□#@0^++            | E | 150   | 20                            | 0.3                 | 30            | 300           | 600            | 8            | 10           | 10            | 0.165                             | 0.742                                | 0.667                                | 0.297                                 | 0.222                                | 0.200                                | 0.089                                 |
| TBJV157*020L□#@0^++            | V | 150   | 20                            | 0.08                | 30            | 300           | 600            | 8            | 10           | 12            | 0.250                             | 1.768                                | 1.591                                | 0.707                                 | 0.141                                | 0.127                                | 0.057                                 |
| TBJA334*025C□#@0^++            | A | 0.33  | 25                            | 15                  | 0.083         | 0.825         | 0.99           | 4            | 6            | 6             | 0.075                             | 0.071                                | 0.064                                | 0.028                                 | 1.061                                | 0.955                                | 0.424                                 |
| TBJA474*025C□#@0^++            | A | 0.47  | 25                            | 14                  | 0.118         | 1.175         | 1.41           | 4            | 6            | 6             | 0.075                             | 0.073                                | 0.066                                | 0.029                                 | 1.025                                | 0.922                                | 0.410                                 |
| TBJA474*025L□#@0^++            | A | 0.47  | 25                            | 7                   | 0.118         | 1.175         | 2.35           | 4            | 6            | 6             | 0.075                             | 0.104                                | 0.093                                | 0.041                                 | 0.725                                | 0.652                                | 0.290                                 |
| TBJA684*025C□#@0^++            | A | 0.68  | 25                            | 10                  | 0.68          | 6.8           | 13.6           | 4            | 6            | 8             | 0.075                             | 0.087                                | 0.078                                | 0.035                                 | 0.866                                | 0.779                                | 0.346                                 |
| TBJA684*025L□#@0^++            | A | 0.68  | 25                            | 6                   | 0.17          | 1.7           | 3.4            | 4            | 6            | 6             | 0.075                             | 0.112                                | 0.101                                | 0.045                                 | 0.671                                | 0.604                                | 0.268                                 |
| TBJB684*025C□#@0^++            | B | 0.68  | 25                            | 7.5                 | 0.17          | 1.7           | 2.04           | 4            | 6            | 6             | 0.085                             | 0.106                                | 0.096                                | 0.043                                 | 0.798                                | 0.719                                | 0.319                                 |
| TBJA105*025C□#@0^++            | A | 1   | 25                            | 8                   | 0.25          | 2.5           | 5              | 4            | 6            | 8             | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJB105*025C□#@0^++            | B | 1   | 25                            | 6.5                 | 0.25          | 2.5           | 3              | 4            | 6            | 6             | 0.085                             | 0.114                                | 0.103                                | 0.046                                 | 0.743                                | 0.669                                | 0.297                                 |
| TBJA155*025C□#@0^++            | A | 1.5   | 25                            | 7.5                 | 0.375         | 3.75          | 7.5            | 6            | 8            | 10            | 0.075                             | 0.100                                | 0.090                                | 0.040                                 | 0.750                                | 0.675                                | 0.300                                 |
| TBJA155*025L□#@0^++            | A | 1.5   | 25                            | 3                   | 0.375         | 3.75          | 7.5            | 6            | 8            | 10            | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJB155*025C□#@0^++            | B | 1.5   | 25                            | 6.5                 | 0.375         | 3.75          | 4.5            | 6            | 8            | 9             | 0.085                             | 0.114                                | 0.103                                | 0.046                                 | 0.743                                | 0.669                                | 0.297                                 |
| TBJB155*025L□#@0^++            | B | 1.5   | 25                            | 1.8                 | 0.375         | 3.75          | 7.5            | 6            | 9            | 10            | 0.085                             | 0.217                                | 0.196                                | 0.087                                 | 0.391                                | 0.352                                | 0.156                                 |
| TBJB225*025C□#@0^++            | B | 2.2   | 25                            | 4.5                 | 0.55          | 5.5           | 11             | 6            | 8            | 10            | 0.085                             | 0.137                                | 0.124                                | 0.055                                 | 0.618                                | 0.557                                | 0.247                                 |
| TBJB225*025L□#@0^++            | B | 2.2   | 25                            | 0.9                 | 0.55          | 5.5           | 11             | 6            | 9            | 10            | 0.085                             | 0.307                                | 0.277                                | 0.123                                 | 0.277                                | 0.249                                | 0.111                                 |
| TBJC225*025C□#@0^++            | C | 2.2   | 25                            | 3.5                 | 0.55          | 5.5           | 6.6            | 6            | 9            | 9             | 0.110                             | 0.177                                | 0.160                                | 0.071                                 | 0.620                                | 0.558                                | 0.248                                 |
| TBJA335*025C□#@0^++            | A | 3.3   | 25                            | 1.5                 | 0.825         | 8.25          | 16.5           | 6            | 9            | 10            | 0.075                             | 0.224                                | 0.201                                | 0.089                                 | 0.335                                | 0.302                                | 0.134                                 |
| TBJA335*025L□#@0^++            | A | 3.3   | 25                            | 1                   | 0.825         | 8.25          | 16.5           | 6            | 9            | 10            | 0.075                             | 0.274                                | 0.246                                | 0.110                                 | 0.274                                | 0.246                                | 0.110                                 |
| TBJB335*025C□#@0^++            | B | 3.3   | 25                            | 3.5                 | 0.825         | 8.25          | 16.5           | 6            | 8            | 10            | 0.085                             | 0.156                                | 0.140                                | 0.062                                 | 0.545                                | 0.491                                | 0.218                                 |
| TBJB335*025L□#@0^++            | B | 3.3   | 25                            | 0.75                | 0.825         | 8.25          | 16.5           | 6            | 9            | 10            | 0.085                             | 0.337                                | 0.303                                | 0.135                                 | 0.252                                | 0.227                                | 0.101                                 |
| TBJC335*025C□#@0^++            | C | 3.3   | 25                            | 3.5                 | 0.825         | 8.25          | 9.9            | 6            | 8            | 9             | 0.110                             | 0.177                                | 0.160                                | 0.071                                 | 0.620                                | 0.558                                | 0.248                                 |
| TBJA475*025C□#@0^++            | A | 4.7   | 25                            | 2.8                 | 1.175         | 11.75         | 23.5           | 6            | 9            | 10            | 0.075                             | 0.164                                | 0.147                                | 0.065                                 | 0.458                                | 0.412                                | 0.183                                 |
| TBJB475*025C□#@0^++            | B | 4.7   | 25                            | 2.8                 | 1.175         | 11.75         | 23.5           | 6            | 8            | 10            | 0.085                             | 0.174                                | 0.157                                | 0.070                                 | 0.488                                | 0.439                                | 0.195                                 |
| TBJB475*025L□#@0^++            | B | 4.7   | 25                            | 1.5                 | 1.175         | 11.75         | 23.5           | 6            | 8            | 10            | 0.085                             | 0.238                                | 0.214                                | 0.095                                 | 0.357                                | 0.321                                | 0.143                                 |
| TBJC475*025C□#@0^++            | C | 4.7   | 25                            | 2.5                 | 1.175         | 11.75         | 14.1           | 6            | 9            | 9             | 0.110                             | 0.210                                | 0.189                                | 0.084                                 | 0.524                                | 0.472                                | 0.210                                 |
| TBJB685*025C□#@0^++            | B | 6.8   | 25                            | 2.8                 | 1.7           | 17            | 34             | 6            | 8            | 10            | 0.085                             | 0.174                                | 0.157                                | 0.070                                 | 0.488                                | 0.439                                | 0.195                                 |
| TBJB685*025L□#@0^++            | B | 6.8   | 25                            | 0.7                 | 1.7           | 17            | 34             | 6            | 9            | 10            | 0.085                             | 0.348                                | 0.314                                | 0.139                                 | 0.244                                | 0.220                                | 0.098                                 |
| TBJC685*025C□#@0^++            | C | 6.8   | 25                            | 2                   | 1.7           | 17            | 34             | 6            | 8            | 10            | 0.110                             | 0.235                                | 0.211                                | 0.094                                 | 0.469                                | 0.422                                | 0.188                                 |
| TBJC685*025L□#@0^++            | C | 6.8   | 25                            | 0.5                 | 1.7           | 17            | 34             | 6            | 9            | 10            | 0.110                             | 0.469                                | 0.422                                | 0.188                                 | 0.235                                | 0.211                                | 0.094                                 |
| TBJD685*025C□#@0^++            | D | 6.8   | 25                            | 1.4                 | 1.7           | 17            | 20.4           | 6            | 9            | 9             | 0.150                             | 0.327                                | 0.295                                | 0.131                                 | 0.458                                | 0.412                                | 0.183                                 |
| TBJC106*025C□#@0^++            | C | 10  | 25                            | 1.8                 | 2.5           | 25            | 50             | 6            | 8            | 10            | 0.110                             | 0.247                                | 0.222                                | 0.099                                 | 0.445                                | 0.400                                | 0.178                                 |
| TBJC106*025L□#@0^++            | C | 10  | 25                            | 0.5                 | 2.5           | 25            | 50             | 6            | 8            | 10            | 0.110                             | 0.469                                | 0.422                                | 0.188                                 | 0.235                                | 0.211                                | 0.094                                 |
| TBJD106*025C□#@0^++            | D | 10  | 25                            | 1.2                 | 2.5           | 25            | 30             | 6            | 8            | 9             | 0.150                             | 0.354                                | 0.318                                | 0.141                                 | 0.424                                | 0.382                                | 0.170                                 |
| TBJC156*025C□#@0^++            | C | 15  | 25                            | 0.3                 | 3.75          | 37.5          | 75             | 6            | 9            | 10            | 0.110                             | 0.606                                | 0.545                                | 0.242                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJC156*025L□#@0^++            | C | 15  | 25                            | 0.22                | 3.75          | 37.5          | 75             | 6            | 9            | 10            | 0.110                             | 0.707                                | 0.636                                | 0.283                                 | 0.156                                | 0.140                                | 0.062                                 |
| TBJD156*025C□#@0^++            | D | 15  | 25                            | 1                   | 3.75          | 37.5          | 45             | 6            | 9            | 9             | 0.150                             | 0.387                                | 0.349                                | 0.155                                 | 0.387                                | 0.349                                | 0.155                                 |
| TBJD156*025L□#@0^++            | D | 15  | 25                            | 0.3                 | 3.75          | 37.5          | 75             | 6            | 8            | 8             | 0.150                             | 0.707                                | 0.636                                | 0.283                                 | 0.212                                | 0.191                                | 0.085                                 |
| TBJC226*025C□#@0^++            | C | 22  | 25                            | 1.4                 | 5.5           | 55            | 110            | 6            | 8            | 10            | 0.110                             | 0.280                                | 0.252                                | 0.112                                 | 0.392                                | 0.353                                | 0.157                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                              |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |                  |              | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                              | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJC226*025L□#@0^++            | C | 22  | 25                            | 0.275                        | 5.5           | 55            | 110            | 6            | 8                | 10           | 0.110                             | 0.632                                | 0.569                                | 0.253                                 | 0.174                                | 0.157                                | 0.070                                 |
| TBJD226*025C□#@0^++            | D | 22  | 25                            | 0.9                          | 5.5           | 55            | 110            | 6            | 8                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD226*025L□#@0^++            | D | 22  | 25                            | 0.2                          | 5.5           | 55            | 110            | 6            | 8                | 10           | 0.150                             | 0.866                                | 0.779                                | 0.346                                 | 0.173                                | 0.156                                | 0.069                                 |
| TBJD336*025C□#@0^++            | D | 33  | 25                            | 0.9                          | 8.25          | 82.5          | 165            | 6            | 8                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD336*025L□#@0^++            | D | 33  | 25                            | 0.1                          | 8.25          | 82.5          | 165            | 6            | 8                | 10           | 0.150                             | 1.225                                | 1.102                                | 0.490                                 | 0.122                                | 0.110                                | 0.049                                 |
| TBJE336*025C□#@0^++            | E | 33  | 25                            | 0.9                          | 8.25          | 82.5          | 165            | 6            | 8                | 10           | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE336*025L□#@0^++            | E | 33  | 25                            | 0.3                          | 8.25          | 82.5          | 165            | 6            | 8                | 10           | 0.165                             | 0.742                                | 0.667                                | 0.297                                 | 0.222                                | 0.200                                | 0.089                                 |
| TBJD476*025C□#@0^++            | D | 47  | 25                            | 0.9                          | 11.75         | 117.5         | 235            | 6            | 8                | 10           | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD476*025L□#@0^++            | D | 47  | 25                            | 0.25                         | 11.75         | 117.5         | 235            | 6            | 8                | 10           | 0.150                             | 0.775                                | 0.697                                | 0.310                                 | 0.194                                | 0.174                                | 0.077                                 |
| TBJE476*025C□#@0^++            | E | 47  | 25                            | 0.1                          | 11.75         | 117.5         | 235            | 6            | 9                | 10           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJE476*025L□#@0^++            | E | 47  | 25                            | 0.08                         | 11.75         | 117.5         | 235            | 6            | 9                | 10           | 0.165                             | 1.436                                | 1.293                                | 0.574                                 | 0.115                                | 0.103                                | 0.046                                 |
| TBJE686*025C□#@0^++            | E | 68  | 25                            | 0.2                          | 17            | 170           | 340            | 6            | 9                | 10           | 0.165                             | 0.908                                | 0.817                                | 0.363                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJE686*025L□#@0^++            | E | 68  | 25                            | 0.125                        | 17            | 170           | 340            | 6            | 9                | 10           | 0.165                             | 1.149                                | 1.034                                | 0.460                                 | 0.144                                | 0.129                                | 0.057                                 |
| TBJV686*025L□#@0^++            | V | 68  | 25                            | 0.095                        | 17            | 170           | 340            | 6            | 9                | 10           | 0.250                             | 1.622                                | 1.460                                | 0.649                                 | 0.154                                | 0.139                                | 0.062                                 |
| TBJV107*025L□#@0^++            | V | 100   | 25                            | 0.1                          | 25            | 250           | 500            | 8            | 10               | 12           | 0.250                             | 1.581                                | 1.423                                | 0.632                                 | 0.158                                | 0.142                                | 0.063                                 |
| TBJA104*035C□#@0^++            | A | 0.1   | 35                            | 24                           | 0.035         | 0.35          | 0.42           | 4            | 6                | 6            | 0.075                             | 0.056                                | 0.050                                | 0.022                                 | 1.342                                | 1.207                                | 0.537                                 |
| TBJA154*035C□#@0^++            | A | 0.15  | 35                            | 21                           | 0.5           | 5             | 10             | 4            | 6                | 6            | 0.075                             | 0.060                                | 0.054                                | 0.024                                 | 1.255                                | 1.129                                | 0.502                                 |
| TBJA224*035C□#@0^++            | A | 0.22  | 35                            | 18                           | 0.5           | 5             | 10             | 4            | 6                | 6            | 0.075                             | 0.065                                | 0.058                                | 0.026                                 | 1.162                                | 1.046                                | 0.465                                 |
| TBJA224*035L□#@0^++            | A | 0.22  | 35                            | 6                            | 0.077         | 0.77          | 1.54           | 4            | 6                | 6            | 0.075                             | 0.112                                | 0.101                                | 0.045                                 | 0.671                                | 0.604                                | 0.268                                 |
| TBJA334*035C□#@0^++            | A | 0.33  | 35                            | 15                           | 0.5           | 5             | 10             | 4            | 6                | 6            | 0.075                             | 0.071                                | 0.064                                | 0.028                                 | 1.061                                | 0.955                                | 0.424                                 |
| TBJA334*035L□#@0^++            | A | 0.33  | 35                            | 6                            | 0.116         | 1.155         | 2.31           | 4            | 6                | 6            | 0.075                             | 0.112                                | 0.101                                | 0.045                                 | 0.671                                | 0.604                                | 0.268                                 |
| TBJA474*035C□#@0^++            | A | 0.47  | 35                            | 12                           | 0.165         | 1.645         | 3.29           | 4            | 6                | 8            | 0.075                             | 0.079                                | 0.071                                | 0.032                                 | 0.949                                | 0.854                                | 0.379                                 |
| TBJA474*035L□#@0^++            | A | 0.47  | 35                            | 6                            | 0.165         | 1.645         | 3.29           | 4            | 6                | 6            | 0.075                             | 0.112                                | 0.101                                | 0.045                                 | 0.671                                | 0.604                                | 0.268                                 |
| TBJB474*035C□#@0^++            | B | 0.47  | 35                            | 10                           | 0.165         | 1.645         | 1.974          | 4            | 6                | 6            | 0.085                             | 0.092                                | 0.083                                | 0.037                                 | 0.922                                | 0.830                                | 0.369                                 |
| TBJB474*035L□#@0^++            | B | 0.47  | 35                            | 4                            | 0.165         | 1.645         | 3.29           | 4            | 6                | 6            | 0.085                             | 0.146                                | 0.131                                | 0.058                                 | 0.583                                | 0.525                                | 0.233                                 |
| TBJA684*035C□#@0^++            | A | 0.68  | 35                            | 8                            | 0.238         | 2.38          | 4.76           | 4            | 6                | 8            | 0.075                             | 0.097                                | 0.087                                | 0.039                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJA684*035L□#@0^++            | A | 0.68  | 35                            | 6                            | 0.238         | 2.38          | 4.76           | 4            | 6                | 6            | 0.075                             | 0.112                                | 0.101                                | 0.045                                 | 0.671                                | 0.604                                | 0.268                                 |
| TBJB684*035C□#@0^++            | B | 0.68  | 35                            | 8                            | 0.238         | 2.38          | 2.856          | 4            | 6                | 6            | 0.085                             | 0.103                                | 0.093                                | 0.041                                 | 0.825                                | 0.742                                | 0.330                                 |
| TBJA105*035C□#@0^++            | A | 1   | 35                            | 7.5                          | 0.35          | 3.5           | 7              | 4            | 6                | 6            | 0.075                             | 0.100                                | 0.090                                | 0.040                                 | 0.750                                | 0.675                                | 0.300                                 |
| TBJA105*035L□#@0^++            | A | 1   | 35                            | 3                            | 0.35          | 3.5           | 7              | 4            | 6                | 6            | 0.075                             | 0.158                                | 0.142                                | 0.063                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJB105*035C□#@0^++            | B | 1   | 35                            | 6.5                          | 0.35          | 3.5           | 4.2            | 4            | 6                | 6            | 0.085                             | 0.114                                | 0.103                                | 0.046                                 | 0.743                                | 0.669                                | 0.297                                 |
| TBJB105*035L□#@0^++            | B | 1   | 35                            | 2                            | 0.35          | 3.5           | 7              | 4            | 6                | 6            | 0.085                             | 0.206                                | 0.186                                | 0.082                                 | 0.412                                | 0.371                                | 0.165                                 |
| TBJA155*035C□#@0^++            | A | 1.5   | 35                            | 7.5                          | 0.525         | 5.25          | 10.5           | 6            | 8                | 9            | 0.075                             | 0.100                                | 0.090                                | 0.040                                 | 0.750                                | 0.675                                | 0.300                                 |
| TBJB155*035C□#@0^++            | B | 1.5   | 35                            | 5.2                          | 0.525         | 5.25          | 10.5           | 6            | 8                | 9            | 0.085                             | 0.128                                | 0.115                                | 0.051                                 | 0.665                                | 0.598                                | 0.266                                 |
| TBJB155*035L□#@0^++            | B | 1.5   | 35                            | 2.5                          | 0.525         | 5.25          | 10.5           | 6            | 9                | 10           | 0.085                             | 0.184                                | 0.166                                | 0.074                                 | 0.461                                | 0.415                                | 0.184                                 |
| TBJC155*035C□#@0^++            | C | 1.5   | 35                            | 4.5                          | 0.525         | 5.25          | 6.3            | 6            | 8                | 9            | 0.110                             | 0.156                                | 0.141                                | 0.063                                 | 0.704                                | 0.633                                | 0.281                                 |
| TBJA225*035C□#@0^++            | A | 2.2   | 35                            | 4.5                          | 0.77          | 7.7           | 15.4           | 6            | 9                | 9            | 0.075                             | 0.129                                | 0.116                                | 0.052                                 | 0.581                                | 0.523                                | 0.232                                 |
| TBJA225*035L□#@0^++            | A | 2.2   | 35                            | 1.5                          | 0.77          | 7.7           | 15.4           | 6            | 9                | 10           | 0.075                             | 0.224                                | 0.201                                | 0.089                                 | 0.335                                | 0.302                                | 0.134                                 |
| TBJB225*035C□#@0^++            | B | 2.2   | 35                            | 4.2                          | 0.77          | 7.7           | 15.4           | 6            | 8                | 9            | 0.085                             | 0.142                                | 0.128                                | 0.057                                 | 0.597                                | 0.538                                | 0.239                                 |
| TBJB225*035L□#@0^++            | B | 2.2   | 35                            | 2                            | 0.77          | 7.7           | 15.4           | 6            | 8                | 9            | 0.085                             | 0.206                                | 0.186                                | 0.082                                 | 0.412                                | 0.371                                | 0.165                                 |
| TBJC225*035C□#@0^++            | C | 2.2   | 35                            | 3.5                          | 0.77          | 7.7           | 9.24           | 6            | 8                | 9            | 0.110                             | 0.177                                | 0.160                                | 0.071                                 | 0.620                                | 0.558                                | 0.248                                 |
| TBJC225*035L□#@0^++            | C | 2.2   | 35                            | 1                            | 0.77          | 7.7           | 15.4           | 6            | 9                | 10           | 0.110                             | 0.332                                | 0.298                                | 0.133                                 | 0.332                                | 0.298                                | 0.133                                 |
| TBJB335*035C□#@0^++            | B | 3.3   | 35                            | 3.5                          | 1.155         | 11.55         | 23.1           | 6            | 8                | 9            | 0.085                             | 0.156                                | 0.140                                | 0.062                                 | 0.545                                | 0.491                                | 0.218                                 |
| TBJB335*035L□#@0^++            | B | 3.3   | 35                            | 1                            | 1.155         | 11.55         | 23.1           | 6            | 9                | 10           | 0.085                             | 0.292                                | 0.262                                | 0.117                                 | 0.292                                | 0.262                                | 0.117                                 |
| TBJC335*035C□#@0^++            | C | 3.3   | 35                            | 2.5                          | 1.155         | 11.55         | 13.86          | 6            | 8                | 9            | 0.110                             | 0.210                                | 0.189                                | 0.084                                 | 0.524                                | 0.472                                | 0.210                                 |
| TBJC335*035L□#@0^++            | C | 3.3   | 35                            | 0.7                          | 1.155         | 11.55         | 23.1           | 6            | 9                | 10           | 0.110                             | 0.396                                | 0.357                                | 0.159                                 | 0.277                                | 0.250                                | 0.111                                 |
| TBJB475*035C□#@0^++            | B | 4.7   | 35                            | 3.1                          | 1.645         | 16.45         | 32.9           | 6            | 8                | 9            | 0.085                             | 0.166                                | 0.149                                | 0.066                                 | 0.513                                | 0.462                                | 0.205                                 |
| TBJB475*035L□#@0^++            | B | 4.7   | 35                            | 0.7                          | 1.645         | 16.45         | 32.9           | 6            | 8                | 8            | 0.085                             | 0.348                                | 0.314                                | 0.139                                 | 0.244                                | 0.220                                | 0.098                                 |
| TBJC475*035C□#@0^++            | C | 4.7   | 35                            | 2.2                          | 1.645         | 16.45         | 32.9           | 6            | 8                | 9            | 0.110                             | 0.224                                | 0.201                                | 0.089                                 | 0.492                                | 0.443                                | 0.197                                 |
| TBJC475*035L□#@0^++            | C | 4.7   | 35                            | 0.6                          | 1.645         | 16.45         | 32.9           | 6            | 8                | 9            | 0.110                             | 0.428                                | 0.385                                | 0.171                                 | 0.257                                | 0.231                                | 0.103                                 |
| TBJD475*035C□#@0^++            | D | 4.7   | 35                            | 1.5                          | 1.645         | 16.45         | 19.74          | 6            | 8                | 9            | 0.150                             | 0.316                                | 0.285                                | 0.126                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJD475*035L□#@0^++            | D | 4.7   | 35                            | 0.5                          | 1.645         | 16.45         | 32.9           | 6            | 8                | 9            | 0.150                             | 0.548                                | 0.493                                | 0.219                                 | 0.274                                | 0.246                                | 0.110                                 |
| TBJC685*035C□#@0^++            | C | 6.8   | 35                            | 1.8                          | 2.38          | 23.8          | 47.6           | 6            | 8                | 9            | 0.110                             | 0.247                                | 0.222                                | 0.099                                 | 0.445                                | 0.400                                | 0.178                                 |
| TBJC685*035L□#@0^++            | C | 6.8   | 35                            | 0.35                         | 2.38          | 23.8          | 47.6           | 6            | 9                | 10           | 0.110                             | 0.561                                | 0.505                                | 0.224                                 | 0.196                                | 0.177                                | 0.078                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

# TBJ Series

## COTS-Plus



| RATING & PART NUMBER REFERENCE |   | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                              |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|---|---|-------------------------------|------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |   | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>Ohms @ +25°C | DCL max       |               |                | DF Max       |                  |              | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |   |   |                               |                              | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJD685*035C□#@0^++            | D | 6.8   | 35                            | 1.3                          | 2.38          | 23.8          | 28.56          | 6            | 9                | 9            | 0.150                             | 0.340                                | 0.306                                | 0.136                                 | 0.442                                | 0.397                                | 0.177                                 |
| TBJD685*035L□#@0^++            | D | 6.8   | 35                            | 0.5                          | 2.38          | 23.8          | 47.6           | 6            | 9                | 9            | 0.150                             | 0.548                                | 0.493                                | 0.219                                 | 0.274                                | 0.246                                | 0.110                                 |
| TBJC106*035C□#@0^++            | C | 10  | 35                            | 1.6                          | 3.5           | 35            | 70             | 6            | 9                | 9            | 0.110                             | 0.262                                | 0.236                                | 0.105                                 | 0.420                                | 0.378                                | 0.168                                 |
| TBJC106*035L□#@0^++            | C | 10  | 35                            | 0.6                          | 3.5           | 35            | 70             | 6            | 9                | 9            | 0.110                             | 0.428                                | 0.385                                | 0.171                                 | 0.257                                | 0.231                                | 0.103                                 |
| TBJD106*035C□#@0^++            | D | 10  | 35                            | 1                            | 3.5           | 35            | 70             | 6            | 9                | 9            | 0.150                             | 0.387                                | 0.349                                | 0.155                                 | 0.387                                | 0.349                                | 0.155                                 |
| TBJD106*035L□#@0^++            | D | 10  | 35                            | 0.3                          | 3.5           | 35            | 70             | 6            | 9                | 9            | 0.150                             | 0.707                                | 0.636                                | 0.283                                 | 0.212                                | 0.191                                | 0.085                                 |
| TBJE106*035C□#@0^++            | E | 10  | 35                            | 0.25                         | 3.5           | 35            | 70             | 6            | 9                | 10           | 0.165                             | 0.812                                | 0.731                                | 0.325                                 | 0.203                                | 0.183                                | 0.081                                 |
| TBJE106*035L□#@0^++            | E | 10  | 35                            | 0.2                          | 3.5           | 35            | 70             | 6            | 9                | 10           | 0.165                             | 0.908                                | 0.817                                | 0.363                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJC156*035C□#@0^++            | C | 15  | 35                            | 1.4                          | 5.25          | 52.5          | 105            | 6            | 9                | 9            | 0.110                             | 0.280                                | 0.252                                | 0.112                                 | 0.392                                | 0.353                                | 0.157                                 |
| TBJC156*035L□#@0^++            | C | 15  | 35                            | 0.35                         | 5.25          | 52.5          | 105            | 6            | 9                | 10           | 0.110                             | 0.561                                | 0.505                                | 0.224                                 | 0.196                                | 0.177                                | 0.078                                 |
| TBJD156*035C□#@0^++            | D | 15  | 35                            | 0.9                          | 5.25          | 52.5          | 105            | 6            | 9                | 9            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD156*035L□#@0^++            | D | 15  | 35                            | 0.3                          | 5.25          | 52.5          | 105            | 6            | 9                | 9            | 0.150                             | 0.707                                | 0.636                                | 0.283                                 | 0.212                                | 0.191                                | 0.085                                 |
| TBJD226*035C□#@0^++            | D | 22  | 35                            | 0.9                          | 7.7           | 77            | 154            | 6            | 9                | 9            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD226*035L□#@0^++            | D | 22  | 35                            | 0.4                          | 7.7           | 77            | 154            | 6            | 9                | 9            | 0.150                             | 0.612                                | 0.551                                | 0.245                                 | 0.245                                | 0.220                                | 0.098                                 |
| TBJE226*035C□#@0^++            | E | 22  | 35                            | 0.9                          | 7.7           | 77            | 154            | 6            | 9                | 9            | 0.165                             | 0.428                                | 0.385                                | 0.171                                 | 0.385                                | 0.347                                | 0.154                                 |
| TBJE226*035L□#@0^++            | E | 22  | 35                            | 0.3                          | 7.7           | 77            | 154            | 6            | 9                | 9            | 0.165                             | 0.742                                | 0.667                                | 0.297                                 | 0.222                                | 0.200                                | 0.089                                 |
| TBJD336*035C□#@0^++            | D | 33  | 35                            | 0.9                          | 11.55         | 115.5         | 231            | 6            | 9                | 9            | 0.150                             | 0.408                                | 0.367                                | 0.163                                 | 0.367                                | 0.331                                | 0.147                                 |
| TBJD336*035L□#@0^++            | D | 33  | 35                            | 0.3                          | 11.55         | 115.5         | 231            | 6            | 9                | 9            | 0.150                             | 0.707                                | 0.636                                | 0.283                                 | 0.212                                | 0.191                                | 0.085                                 |
| TBJE336*035C□#@0^++            | E | 33  | 35                            | 0.25                         | 11.55         | 115.5         | 231            | 6            | 9                | 10           | 0.165                             | 0.812                                | 0.731                                | 0.325                                 | 0.203                                | 0.183                                | 0.081                                 |
| TBJE336*035L□#@0^++            | E | 33  | 35                            | 0.1                          | 11.55         | 115.5         | 231            | 6            | 8                | 10           | 0.165                             | 1.285                                | 1.156                                | 0.514                                 | 0.128                                | 0.116                                | 0.051                                 |
| TBJV336*035L□#@0^++            | V | 33  | 35                            | 0.2                          | 11.55         | 115.5         | 231            | 6            | 9                | 10           | 0.250                             | 1.118                                | 1.006                                | 0.447                                 | 0.224                                | 0.201                                | 0.089                                 |
| TBJE476*035C□#@0^++            | E | 47  | 35                            | 0.25                         | 16.45         | 164.5         | 329            | 6            | 8                | 10           | 0.165                             | 0.812                                | 0.731                                | 0.325                                 | 0.203                                | 0.183                                | 0.081                                 |
| TBJE476*035L□#@0^++            | E | 47  | 35                            | 0.2                          | 16.45         | 164.5         | 329            | 6            | 9                | 9            | 0.165                             | 0.908                                | 0.817                                | 0.363                                 | 0.182                                | 0.163                                | 0.073                                 |
| TBJV476*035C□#@0^++            | V | 47  | 35                            | 0.4                          | 16.45         | 164.5         | 329            | 6            | 9                | 10           | 0.250                             | 0.791                                | 0.712                                | 0.316                                 | 0.316                                | 0.285                                | 0.126                                 |
| TBJV476*035L□#@0^++            | V | 47  | 35                            | 0.2                          | 16.45         | 164.5         | 329            | 6            | 10               | 10           | 0.250                             | 1.118                                | 1.006                                | 0.447                                 | 0.224                                | 0.201                                | 0.089                                 |
| TBJV686*035C□#@0^++            | V | 68  | 35                            | 0.2                          | 23.8          | 238           | 476            | 6            | 9                | 10           | 0.250                             | 1.118                                | 1.006                                | 0.447                                 | 0.224                                | 0.201                                | 0.089                                 |
| TBJV686*035L□#@0^++            | V | 68  | 35                            | 0.15                         | 23.8          | 238           | 476            | 6            | 9                | 10           | 0.250                             | 1.291                                | 1.162                                | 0.516                                 | 0.194                                | 0.174                                | 0.077                                 |
| TBJA104*050C□#@0^++            | A | 0.1   | 50                            | 22                           | 0.05          | 0.5           | 0.6            | 6            | 8                | 8            | 0.075                             | 0.058                                | 0.053                                | 0.023                                 | 1.285                                | 1.156                                | 0.514                                 |
| TBJA154*050C□#@0^++            | A | 0.15  | 50                            | 21                           | 0.02          | 0.2           | 0.4            | 4            | 6                | 6            | 0.075                             | 0.060                                | 0.054                                | 0.024                                 | 1.255                                | 1.129                                | 0.502                                 |
| TBJA154*050L□#@0^++            | A | 0.15  | 50                            | 9                            | 0.075         | 0.75          | 1.5            | 4            | 6                | 6            | 0.075                             | 0.091                                | 0.082                                | 0.037                                 | 0.822                                | 0.739                                | 0.329                                 |
| TBJB154*050C□#@0^++            | B | 0.15  | 50                            | 17                           | 0.075         | 0.75          | 0.9            | 4            | 6                | 6            | 0.085                             | 0.071                                | 0.064                                | 0.028                                 | 1.202                                | 1.082                                | 0.481                                 |
| TBJA224*050C□#@0^++            | A | 0.22  | 50                            | 18                           | 0.11          | 1.1           | 2.2            | 4            | 6                | 6            | 0.075                             | 0.065                                | 0.058                                | 0.026                                 | 1.162                                | 1.046                                | 0.465                                 |
| TBJA224*050L□#@0^++            | A | 0.22  | 50                            | 7                            | 0.11          | 1.1           | 2.2            | 4            | 6                | 6            | 0.075                             | 0.104                                | 0.093                                | 0.041                                 | 0.725                                | 0.652                                | 0.290                                 |
| TBJB224*050C□#@0^++            | B | 0.22  | 50                            | 14                           | 0.11          | 1.1           | 1.32           | 4            | 6                | 6            | 0.085                             | 0.078                                | 0.070                                | 0.031                                 | 1.091                                | 0.982                                | 0.436                                 |
| TBJB334*050C□#@0^++            | B | 0.33  | 50                            | 12                           | 0.165         | 1.65          | 1.98           | 4            | 6                | 6            | 0.085                             | 0.084                                | 0.076                                | 0.034                                 | 1.010                                | 0.909                                | 0.404                                 |
| TBJC474*050C□#@0^++            | C | 0.47  | 50                            | 8                            | 0.235         | 2.35          | 2.82           | 4            | 6                | 6            | 0.110                             | 0.117                                | 0.106                                | 0.047                                 | 0.938                                | 0.844                                | 0.375                                 |
| TBJA684*050C□#@0^++            | A | 0.68  | 50                            | 7.9                          | 0.34          | 3.4           | 6.8            | 4            | 6                | 6            | 0.075                             | 0.097                                | 0.088                                | 0.039                                 | 0.770                                | 0.693                                | 0.308                                 |
| TBJC684*050C□#@0^++            | C | 0.68  | 50                            | 7                            | 0.34          | 3.4           | 4.08           | 4            | 6                | 6            | 0.110                             | 0.125                                | 0.113                                | 0.050                                 | 0.877                                | 0.790                                | 0.351                                 |
| TBJC105*050C□#@0^++            | C | 1   | 50                            | 6                            | 0.5           | 5             | 6              | 4            | 6                | 6            | 0.110                             | 0.135                                | 0.122                                | 0.054                                 | 0.812                                | 0.731                                | 0.325                                 |
| TBJC105*050L□#@0^++            | C | 1   | 50                            | 2.5                          | 0.5           | 5             | 10             | 4            | 6                | 6            | 0.110                             | 0.210                                | 0.189                                | 0.084                                 | 0.524                                | 0.472                                | 0.210                                 |
| TBJC155*050C□#@0^++            | C | 1.5   | 50                            | 5                            | 0.75          | 7.5           | 15             | 6            | 8                | 9            | 0.110                             | 0.148                                | 0.133                                | 0.059                                 | 0.742                                | 0.667                                | 0.297                                 |
| TBJC155*050L□#@0^++            | C | 1.5   | 50                            | 1.5                          | 0.75          | 7.5           | 15             | 6            | 9                | 10           | 0.110                             | 0.271                                | 0.244                                | 0.108                                 | 0.406                                | 0.366                                | 0.162                                 |
| TBJD155*050C□#@0^++            | D | 1.5   | 50                            | 4                            | 0.75          | 7.5           | 9              | 6            | 8                | 9            | 0.150                             | 0.194                                | 0.174                                | 0.077                                 | 0.775                                | 0.697                                | 0.310                                 |
| TBJD225*050C□#@0^++            | D | 2.2   | 50                            | 2.5                          | 1.1           | 11            | 13.2           | 6            | 8                | 9            | 0.150                             | 0.245                                | 0.220                                | 0.098                                 | 0.612                                | 0.551                                | 0.245                                 |
| TBJD225*050L□#@0^++            | D | 2.2   | 50                            | 1.2                          | 1.1           | 11            | 22             | 6            | 9                | 10           | 0.150                             | 0.354                                | 0.318                                | 0.141                                 | 0.424                                | 0.382                                | 0.170                                 |
| TBJD335*050C□#@0^++            | D | 3.3   | 50                            | 2                            | 1.65          | 16.5          | 19.8           | 6            | 9                | 9            | 0.150                             | 0.274                                | 0.246                                | 0.110                                 | 0.548                                | 0.493                                | 0.219                                 |
| TBJD335*050L□#@0^++            | D | 3.3   | 50                            | 0.8                          | 1.65          | 16.5          | 33             | 6            | 9                | 10           | 0.150                             | 0.433                                | 0.390                                | 0.173                                 | 0.346                                | 0.312                                | 0.139                                 |
| TBJD475*050C□#@0^++            | D | 4.7   | 50                            | 1.5                          | 2.35          | 23.5          | 28.2           | 6            | 9                | 9            | 0.150                             | 0.316                                | 0.285                                | 0.126                                 | 0.474                                | 0.427                                | 0.190                                 |
| TBJD475*050L□#@0^++            | D | 4.7   | 50                            | 0.3                          | 2.35          | 23.5          | 47             | 6            | 9                | 9            | 0.150                             | 0.707                                | 0.636                                | 0.283                                 | 0.212                                | 0.191                                | 0.085                                 |
| TBJD685*050C□#@0^++            | D | 6.8   | 50                            | 1                            | 3.4           | 34            | 68             | 6            | 9                | 9            | 0.150                             | 0.387                                | 0.349                                | 0.155                                 | 0.387                                | 0.349                                | 0.155                                 |
| TBJD685*050L□#@0^++            | D | 6.8   | 50                            | 0.5                          | 3.4           | 34            | 68             | 6            | 9                | 9            | 0.150                             | 0.548                                | 0.493                                | 0.219                                 | 0.274                                | 0.246                                | 0.110                                 |
| TBJE106*050C□#@0^++            | E | 10  | 50                            | 0.5                          | 5             | 50            | 100            | 6            | 9                | 10           | 0.165                             | 0.574                                | 0.517                                | 0.230                                 | 0.287                                | 0.259                                | 0.115                                 |
| TBJE106*050L□#@0^++            | E | 10  | 50                            | 0.4                          | 5             | 50            | 100            | 6            | 9                | 10           | 0.165                             | 0.642                                | 0.578                                | 0.257                                 | 0.257                                | 0.231                                | 0.103                                 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**





# TBJ Series

## COTS-Plus




| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating per MIL-PRF-55365/4 |                               |                              |         |       |        |        |             |       | Typical RMS Ripple Data by Rating |                                      |                                      |                                       |                                      |                                      |                                       |
|--------------------------------|------|---|-------------------------------|------------------------------|---------|-------|--------|--------|-------------|-------|-----------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|---------------------------------------|
|                                |      | Cap @ 120Hz<br>µF @ 25°C                                | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>Ohms @ +25°C | DCL max |       |        | DF Max |             |       | Power Dissipation<br>W            | 25°C<br>Ripple Current<br>A (100kHz) | 85°C<br>Ripple Current<br>A (100kHz) | 125°C<br>Ripple Current<br>A (100kHz) | 25°C<br>Ripple Voltage<br>V (100kHz) | 85°C<br>Ripple Voltage<br>V (100kHz) | 125°C<br>Ripple Voltage<br>V (100kHz) |
|                                |      |   |                               |                              | +25°C   | +85°C | +125°C | +25°C  | +(85/125)°C | -55°C |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
|                                |      |   |                               |                              | (µA)    | (µA)  | (µA)   | (%)    | (%)         | (%)   |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| AVX COTS-Plus P/N              | Case |   |                               |                              |         |       |        |        |             |       |                                   |                                      |                                      |                                       |                                      |                                      |                                       |
| TBJV106*050C□#@0^++            | V    | 10  | 50                            | 0.65                         | 5       | 50    | 100    | 3      |             | 0.250 | 0.620                             | 0.558                                | 0.248                                | 0.403                                 | 0.363                                | 0.161                                |                                       |
| TBJD156*050C□#@0^++            | D    | 15  | 50                            | 0.6                          | 7.5     | 75    | 150    | 4      | 6           | 0.150 | 0.500                             | 0.450                                | 0.200                                | 0.300                                 | 0.270                                | 0.120                                |                                       |
| TBJE156*050C□#@0^++            | E    | 15  | 50                            | 0.6                          | 7.5     | 75    | 150    | 8      | 10          | 0.165 | 0.524                             | 0.472                                | 0.210                                | 0.315                                 | 0.283                                | 0.126                                |                                       |
| TBJE156*050L□#@0^++            | E    | 15  | 50                            | 0.25                         | 7.5     | 75    | 150    | 6      | 9           | 0.165 | 0.812                             | 0.731                                | 0.325                                | 0.203                                 | 0.183                                | 0.081                                |                                       |
| TBJV226*050C□#@0^++            | V    | 22  | 50                            | 0.6                          | 11      | 110   | 220    | 8      | 10          | 0.250 | 0.645                             | 0.581                                | 0.258                                | 0.387                                 | 0.349                                | 0.155                                |                                       |
| TBJV226*050L□#@0^++            | V    | 22  | 50                            | 0.39                         | 11      | 110   | 220    | 8      | 10          | 0.250 | 0.801                             | 0.721                                | 0.320                                | 0.312                                 | 0.281                                | 0.125                                |                                       |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**


# TBJ Series

## COTS-Plus – SRC9000 Space Level



### MARKING

#### A, B, C, D, E, U CASE



The TBJ COTS-Plus – SRC9000 series has been refined to incorporate only those commercially up-screened ratings which have been deemed suitable for mission critical and space level applications.

These capacitors have a more conservative design approach when compared to other up-screened components utilizing established CV powders and higher dielectric formation ratios. The DCL is typically 25% lower while still offering aggressive ESR values.

Currently there are 6 case sizes with the wide capac-

ity range available in a given voltage range.

These ratings are available with Weibull grading (B and C), surge current testing MIL-PRF-55365 Rev. G (A, B, C), optional Group A from MIL-PRF-55365, and the extensive SRC9000 space level screening.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.

### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|------------|----------------|------------------------------|------------------------------|------------------------------|------------------------------|--------------|
| A    | 1206     | 3216-18    | 3.20 (0.126)   | 1.60 (0.063)                 | 1.60 (0.063)                 | 1.20 (0.047)                 | 0.80 (0.031)                 | 1.10 (0.043) |
| B    | 1210     | 3528-21    | 3.50 (0.138)   | 2.80 (0.110)                 | 1.90 (0.075)                 | 2.20 (0.087)                 | 0.80 (0.031)                 | 1.40 (0.055) |
| C    | 2312     | 6032-28    | 6.00 (0.236)   | 3.20 (0.126)                 | 2.60 (0.102)                 | 2.20 (0.087)                 | 1.30 (0.051)                 | 2.90 (0.114) |
| D    | 2917     | 7343-31    | 7.30 (0.287)   | 4.30 (0.169)                 | 2.90 (0.114)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| E    | 2917     | 7343-43    | 7.30 (0.287)   | 4.30 (0.169)                 | 4.10 (0.162)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| U    | 2924     | 7361-43    | 7.30 (0.287)   | 6.10 (0.240)                 | 4.10 (0.162)                 | 3.10 (0.120)                 | 1.30 (0.051)                 | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) to 85°C |   |   |  |                                |  |                                |
|-------------|------|--|---|---|--|--------------------------------|--|--------------------------------|
| µF          | Code | 6.3V (J)                                   | 10V (A)                                   | 16V (C)                                   | 20V (D)                                | 25V (E)                        | 35V (V)                                  | 50V (T)                        |
| 0.10        | 104  |  |   |   |  |                                | A(20000)                                 |                                |
| 0.15        | 154  |  |   |   |  |                                | A(6000, 16470)                           |                                |
| 0.22        | 224  |  |   |   |  |                                | A(6000, 13710)                           | A(7000, 7500)                  |
| 0.33        | 334  |  |   |   |  |                                | A(6000, 11280)                           | A(7000)                        |
| 0.47        | 474  |  |   |   |  | A(7000, 9530)                  | A(4000, 9530)                            | B(5000)                        |
| 0.68        | 684  |  |   |   |  | A(6000, 7980)                  | A(6000, 8000)                            | B(2000, 4000)                  |
| 1.0         | 105  |  |   | A(10000)                                  | A(3000, 6630)                          | A(3000, 6630)                  | A(3000, 6630)<br>B(2000, 3400)           | B(2000, 3400)<br>C(3000)       |
| 1.5         | 155  |  | A(7000)                                   |   | A(3000, 5640)                          | A(3000, 5640)<br>B(5000)       | A(2000, 3100)<br>B(2500, 5460)           | C(1500, 2500)                  |
| 2.2         | 225  |  | A(7000)                                   | A(3500, 4550)                             | A(3000, 4550)                          | A(1600, 2900)<br>B(1200, 4550) | B(2000, 4550)                            | C(1000, 1700)<br>D(1200, 2000) |
| 3.3         | 335  |  |   | A(3500, 3750)<br>B(4500)                  | A(2500, 3750)<br>B(1300, 3740)         | B(2000, 3740)                  | B(1000, 3740)<br>C(800, 1840)<br>D(2000) | C(1000, 1400)<br>D(800, 1100)  |
| 4.7         | 475  |  | A(2000, 2900)                             | A(2000, 3160)<br>B(1500, 3160)            | A(1800, 2500)<br>B(1000, 3160)         | B(1000, 3160)                  | B(1500, 2200)<br>C(600, 1410)<br>D(1500) | D(600, 900)                    |
| 6.8         | 685  |  | A(1800, 4000)<br>B(3000)                  | A(1500, 2000)<br>B(1200, 2650)<br>C(2500) | B(1000, 2650)<br>C(2000)               | B(1000, 1500)<br>C(600, 1070)  | C(600, 1070)<br>D(1300)                  | D(700)                         |
| 10          | 106  | A(1500, 2000)<br>B(3000)                   | A(1800, 2200)<br>B(800, 2200)             | B(800, 2200)<br>C(2000)                   | B(1000, 2200)<br>C(500, 800)           | C(600, 800)<br>D(1200)         | C(600, 800)<br>D(250, 800)               | E(300, 700)                    |
| 15          | 156  | A(1500, 2030)<br>B(700, 2030)              | A(1000, 1800)<br>B(600, 2030)<br>C(2000)  | B(800, 2000)                              | B(500, 1400)<br>C(400, 750)<br>D(1100) | C(500, 720)<br>D(300, 720)     | D(225, 720)                              | U(500)                         |
| 22          | 226  | A(900, 1700)<br>B(600, 1880)<br>C(2000)    | B(700, 1800)                              | B(600, 1100)<br>C(350, 700)<br>D(1100)    | C(400, 650)<br>D(150, 650)             | D(300, 650)                    | D(200, 650)                              | U(500)                         |
| 33          | 336  | B(600, 1740)<br>C(1800)                    | B(650, 1000)<br>C(300, 590)<br>D(1100)    | C(300, 590)                               | C(300, 590)<br>D(250, 590)             | D(400, 590)                    | E(250, 590)                              |                                |
| 47          | 476  | B(500, 1620)<br>C(250, 540)                | C(300, 540)<br>D(400)                     | C(350, 540)<br>D(200, 340)                | D(200, 540)                            | D(250, 540)<br>E(150, 540)     | U(200,400)                               |                                |
| 68          | 686  | C(200, 490)                                | C(300, 490)                               | D(150, 490)                               | D(200, 490)<br>E(125, 490)             | U(500)                         |  |                                |
| 100         | 107  | C(300, 440)                                | C(200, 500)<br>D(150, 440)<br>E(100, 440) | D(150, 450)<br>E(150, 450)                | E(150, 300)                            | U(500)                         |  |                                |
| 150         | 157  | C(300, 500)<br>D(150, 400)                 | D(150, 400)<br>E(150, 400)                | E(150, 300)                               | U(250, 500)                            |                                |  |                                |
| 220         | 227  | D(150, 360)                                | D(500)<br>E(150, 360)                     | U(200,500)                                |  |                                |  |                                |
| 330         | 337  | D(400)<br>E(150, 330)                      | E(100, 300)                               | U(200, 400)                               |  |                                |  |                                |
| 470         | 477  | E(200, 250)                                | U(200, 400)                               |   |  |                                |  |                                |
| 680         | 687  | U(250,500)                                 |   |   |  |                                |  |                                |

Available Ratings: ESR limits quoted in brackets (mOhms)

Notes: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards.

# TBJ Series



## COTS-Plus – SRC9000 Space Level

### HOW TO ORDER

#### AVX PART NUMBER:

| TBJ  | D         | 227   | *                     | 035  | R                          | B  | S                                   | Z   | 0                             | 0   | 00  |
|------|-----------|---|-----------------------|--|----------------------------|--|-------------------------------------|---|-------------------------------|---|---|
| Type | Case Size | Capacitance Code  | Capacitance Tolerance | Voltage Code   | ESR                        | Packaging  | Inspection Level                    | Reliability Grade   | Qualification Level           | Termination Finish  | Surge Test Option   |
|      |           | pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | M = ±20%<br>K = ±10%  | 006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | R = Std ESR<br>J = Low ESR | B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle* | S = Std. Conformance<br>L = Group A | Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>Z = Non-ER | 0 = N/A<br><b>9 = SRC9000</b> | H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated<br>7 = Matte Sn (COTS-Plus only) | 00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |

\*Waffle packaging not available for the TBJ U case

For RoHS compliant products, please select correct termination style.

#### SPACE LEVEL OPTIONS TO SRC9000\*:

| TBJ  | D         | 227   | *                     | 035          | R                          | B  | L                | C                             | 9                   | 0  | 45   |
|------|-----------|---|-----------------------|--------------|----------------------------|--|------------------|-------------------------------|---------------------|--|--|
| Type | Case Size | Capacitance Code  | Capacitance Tolerance | Voltage Code | ESR                        | Packaging  | Inspection Level | Reliability Grade             | Qualification Level | Termination Finish   | Surge Test Option                            |
|      |           | pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | M = ±20%<br>K = ±10%  |              | R = Std ESR<br>J = Low ESR | B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle*<br><br>See page 8 for additional packaging options. | L = Group A      | C = 0.01%/1000 hrs. 90% conf. | 9 = SRC9000         | H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated | 45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

\*Waffle packaging not available for the TBJ U case

\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |    |    |    |    |    |    |  |
|------------------------------------|---|-----|----|----|----|----|----|----|--|
| Technical Data:                    | All technical data relate to an ambient temperature of 25°C |     |    |    |    |    |    |    |  |
| Capacitance Range:                 | 0.10 µF to 680 µF   |     |    |    |    |    |    |    |  |
| Capacitance Tolerance:             | ±10%; ±20%  |     |    |    |    |    |    |    |  |
| Leakage Current DCL:               | 0.0075CV  |     |    |    |    |    |    |    |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 6.3 | 10 | 16 | 20 | 25 | 35 | 50 |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 4   | 7  | 10 | 13 | 17 | 23 | 33 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 8   | 13 | 20 | 26 | 32 | 46 | 65 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 5   | 8  | 13 | 16 | 20 | 28 | 40 |  |
| Temperature Range:                 | -55°C to +125°C   |     |    |    |    |    |    |    |  |

# TBJ Series

## COTS-Plus – SRC9000 Space Level



| RATING & PART NUMBER REFERENCE |                           |   | Parametric Specifications by Rating |                                     |                                     |               |               |                |              |              |               | Typical RMS Ripple Data by Rating |                                  |                                  |                                   |                                  |                                  |                                   |
|--------------------------------|---------------------------|---|-------------------------------------|-------------------------------------|-------------------------------------|---------------|---------------|----------------|--------------|--------------|---------------|-----------------------------------|----------------------------------|----------------------------------|-----------------------------------|----------------------------------|----------------------------------|-----------------------------------|
|                                |                           |   | Cap<br>@ 120Hz<br>µF<br>@ 25°C      | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>mOhms<br>@ +25°C | DCL max       |               |                | DF Max       |              |               | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>mA<br>(100kHz) | 85°C<br>Ripple<br>mA<br>(100kHz) | 125°C<br>Ripple<br>mA<br>(100kHz) | 25°C<br>Ripple<br>mV<br>(100kHz) | 85°C<br>Ripple<br>mV<br>(100kHz) | 125°C<br>Ripple<br>mV<br>(100kHz) |
|                                |                           |   |                                     |                                     |                                     | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85°C<br>(%) | +125°C<br>(%) |                                   |                                  |                                  |                                   |                                  |                                  |                                   |
| TBJA106*006 R □ # @ 0 ^ ++     | TBJA106*006 R □ LC 9 ^ 45 | A | 10                                  | 6.3                                 | 2200                                | 0.45          | 4.5           | 9              | 6            | 9            | 10            | 0.075                             | 185                              | 166                              | 74                                | 406                              | 366                              | 162                               |
| TBJA106*006 J □ # @ 0 ^ ++     | TBJA106*006 J □ LC 9 ^ 45 | A | 10                                  | 6.3                                 | 1500                                | 0.45          | 4.5           | 9              | 6            | 9            | 10            | 0.075                             | 224                              | 201                              | 89                                | 335                              | 302                              | 134                               |
| TBJB106*006 R □ # @ 0 ^ ++     | TBJB106*006 R □ LC 9 ^ 45 | B | 10                                  | 6.3                                 | 3000                                | 0.45          | 4.5           | 9              | 6            | 9            | 10            | 0.085                             | 168                              | 151                              | 67                                | 505                              | 454                              | 202                               |
| TBJA156*006 R □ # @ 0 ^ ++     | TBJA156*006 R □ LC 9 ^ 45 | A | 15                                  | 6.3                                 | 2030                                | 0.68          | 6.8           | 13.6           | 6            | 9            | 10            | 0.075                             | 192                              | 173                              | 77                                | 390                              | 351                              | 156                               |
| TBJA156*006 J □ # @ 0 ^ ++     | TBJA156*006 J □ LC 9 ^ 45 | A | 15                                  | 6.3                                 | 1500                                | 0.68          | 6.8           | 13.6           | 6            | 9            | 10            | 0.075                             | 224                              | 201                              | 89                                | 335                              | 302                              | 134                               |
| TBJB156*006 R □ # @ 0 ^ ++     | TBJB156*006 R □ LC 9 ^ 45 | B | 15                                  | 6.3                                 | 2030                                | 0.68          | 6.8           | 13.6           | 6            | 9            | 10            | 0.085                             | 205                              | 184                              | 82                                | 415                              | 374                              | 166                               |
| TBJB156*006 J □ # @ 0 ^ ++     | TBJB156*006 J □ LC 9 ^ 45 | B | 15                                  | 6.3                                 | 700                                 | 0.68          | 6.8           | 13.6           | 6            | 9            | 10            | 0.085                             | 348                              | 314                              | 139                               | 244                              | 220                              | 98                                |
| TBJA226*006 R □ # @ 0 ^ ++     | TBJA226*006 R □ LC 9 ^ 45 | A | 22                                  | 6.3                                 | 1700                                | 0.99          | 9.9           | 19.8           | 6            | 9            | 10            | 0.075                             | 210                              | 189                              | 84                                | 357                              | 321                              | 143                               |
| TBJA226*006 J □ # @ 0 ^ ++     | TBJA226*006 J □ LC 9 ^ 45 | A | 22                                  | 6.3                                 | 900                                 | 0.99          | 9.9           | 19.8           | 6            | 9            | 10            | 0.075                             | 289                              | 260                              | 115                               | 260                              | 234                              | 104                               |
| TBJB226*006 R □ # @ 0 ^ ++     | TBJB226*006 R □ LC 9 ^ 45 | B | 22                                  | 6.3                                 | 1880                                | 0.99          | 9.9           | 19.8           | 6            | 9            | 10            | 0.085                             | 213                              | 191                              | 85                                | 400                              | 360                              | 160                               |
| TBJB226*006 J □ # @ 0 ^ ++     | TBJB226*006 J □ LC 9 ^ 45 | B | 22                                  | 6.3                                 | 600                                 | 0.99          | 9.9           | 19.8           | 6            | 9            | 10            | 0.085                             | 376                              | 339                              | 151                               | 226                              | 203                              | 90                                |
| TBJC226*006 R □ # @ 0 ^ ++     | TBJC226*006 R □ LC 9 ^ 45 | C | 22                                  | 6.3                                 | 2000                                | 0.99          | 9.9           | 19.8           | 6            | 9            | 10            | 0.110                             | 235                              | 211                              | 94                                | 469                              | 422                              | 188                               |
| TBJB336*006 R □ # @ 0 ^ ++     | TBJB336*006 R □ LC 9 ^ 45 | B | 33                                  | 6.3                                 | 1740                                | 1.5           | 15            | 30             | 6            | 9            | 10            | 0.085                             | 221                              | 199                              | 88                                | 385                              | 346                              | 154                               |
| TBJC336*006 J □ # @ 0 ^ ++     | TBJC336*006 J □ LC 9 ^ 45 | B | 33                                  | 6.3                                 | 600                                 | 1.5           | 15            | 30             | 6            | 9            | 10            | 0.085                             | 376                              | 339                              | 151                               | 226                              | 203                              | 90                                |
| TBJC336*006 R □ # @ 0 ^ ++     | TBJC336*006 R □ LC 9 ^ 45 | C | 33                                  | 6.3                                 | 1800                                | 1.5           | 15            | 30             | 6            | 9            | 10            | 0.110                             | 247                              | 222                              | 99                                | 445                              | 400                              | 178                               |
| TBJB476*006 R □ # @ 0 ^ ++     | TBJB476*006 R □ LC 9 ^ 45 | B | 47                                  | 6.3                                 | 1620                                | 2.1           | 21            | 42             | 6            | 9            | 10            | 0.085                             | 229                              | 206                              | 92                                | 371                              | 334                              | 148                               |
| TBJB476*006 J □ # @ 0 ^ ++     | TBJB476*006 J □ LC 9 ^ 45 | B | 47                                  | 6.3                                 | 500                                 | 2.1           | 21            | 42             | 6            | 9            | 10            | 0.085                             | 412                              | 371                              | 165                               | 206                              | 186                              | 82                                |
| TBJC476*006 R □ # @ 0 ^ ++     | TBJC476*006 R □ LC 9 ^ 45 | C | 47                                  | 6.3                                 | 540                                 | 2.1           | 21            | 42             | 6            | 9            | 10            | 0.110                             | 451                              | 406                              | 181                               | 244                              | 219                              | 97                                |
| TBJC476*006 J □ # @ 0 ^ ++     | TBJC476*006 J □ LC 9 ^ 45 | C | 47                                  | 6.3                                 | 250                                 | 2.1           | 21            | 42             | 6            | 9            | 10            | 0.110                             | 663                              | 597                              | 265                               | 166                              | 149                              | 66                                |
| TBJC686*006 R □ # @ 0 ^ ++     | TBJC686*006 R □ LC 9 ^ 45 | C | 68                                  | 6.3                                 | 490                                 | 3.1           | 31            | 62             | 6            | 9            | 10            | 0.110                             | 474                              | 426                              | 190                               | 232                              | 209                              | 93                                |
| TBJC686*006 J □ # @ 0 ^ ++     | TBJC686*006 J □ LC 9 ^ 45 | C | 68                                  | 6.3                                 | 200                                 | 3.1           | 31            | 62             | 6            | 9            | 10            | 0.110                             | 742                              | 667                              | 297                               | 148                              | 133                              | 59                                |
| TBJC107*006 R □ # @ 0 ^ ++     | TBJC107*006 R □ LC 9 ^ 45 | C | 100                                 | 6.3                                 | 440                                 | 4.5           | 45            | 90             | 6            | 9            | 10            | 0.110                             | 500                              | 450                              | 200                               | 220                              | 198                              | 88                                |
| TBJC107*006 J □ # @ 0 ^ ++     | TBJC107*006 J □ LC 9 ^ 45 | C | 100                                 | 6.3                                 | 300                                 | 4.5           | 45            | 90             | 6            | 9            | 10            | 0.110                             | 606                              | 545                              | 242                               | 182                              | 163                              | 73                                |
| TBJC157*006 R □ # @ 0 ^ ++     | TBJC157*006 R □ LC 9 ^ 45 | C | 150                                 | 6.3                                 | 500                                 | 6.8           | 68            | 136            | 8            | 10           | 12            | 0.110                             | 469                              | 422                              | 188                               | 235                              | 211                              | 94                                |
| TBJC157*006 J □ # @ 0 ^ ++     | TBJC157*006 J □ LC 9 ^ 45 | C | 150                                 | 6.3                                 | 300                                 | 6.8           | 68            | 136            | 8            | 10           | 12            | 0.110                             | 606                              | 545                              | 242                               | 182                              | 163                              | 73                                |
| TBJD157*006 R □ # @ 0 ^ ++     | TBJD157*006 R □ LC 9 ^ 45 | D | 150                                 | 6.3                                 | 400                                 | 6.8           | 68            | 136            | 6            | 9            | 10            | 0.150                             | 612                              | 551                              | 245                               | 245                              | 220                              | 98                                |
| TBJD157*006 J □ # @ 0 ^ ++     | TBJD157*006 J □ LC 9 ^ 45 | D | 150                                 | 6.3                                 | 150                                 | 6.8           | 68            | 136            | 6            | 9            | 10            | 0.150                             | 1000                             | 900                              | 400                               | 150                              | 135                              | 60                                |
| TBJD227*006 R □ # @ 0 ^ ++     | TBJD227*006 R □ LC 9 ^ 45 | D | 220                                 | 6.3                                 | 360                                 | 9.9           | 99            | 198            | 8            | 10           | 12            | 0.150                             | 645                              | 581                              | 258                               | 232                              | 209                              | 93                                |
| TBJD227*006 J □ # @ 0 ^ ++     | TBJD227*006 J □ LC 9 ^ 45 | D | 220                                 | 6.3                                 | 150                                 | 9.9           | 99            | 198            | 8            | 10           | 12            | 0.150                             | 1000                             | 900                              | 400                               | 150                              | 135                              | 60                                |
| TBJD337*006 R □ # @ 0 ^ ++     | TBJD337*006 R □ LC 9 ^ 45 | D | 330                                 | 6.3                                 | 400                                 | 14            | 140           | 280            | 8            | 10           | 12            | 0.150                             | 612                              | 551                              | 245                               | 245                              | 220                              | 98                                |
| TBJE337*006 R □ # @ 0 ^ ++     | TBJE337*006 R □ LC 9 ^ 45 | E | 330                                 | 6.3                                 | 330                                 | 14            | 140           | 280            | 8            | 10           | 12            | 0.165                             | 707                              | 636                              | 283                               | 233                              | 210                              | 93                                |
| TBJE337*006 J □ # @ 0 ^ ++     | TBJE337*006 J □ LC 9 ^ 45 | E | 330                                 | 6.3                                 | 150                                 | 14            | 140           | 280            | 8            | 10           | 12            | 0.165                             | 1049                             | 944                              | 420                               | 157                              | 142                              | 63                                |
| TBJE477*006 R □ # @ 0 ^ ++     | TBJE477*006 R □ LC 9 ^ 45 | E | 470                                 | 6.3                                 | 250                                 | 21            | 210           | 420            | 8            | 10           | 12            | 0.165                             | 812                              | 731                              | 325                               | 203                              | 183                              | 81                                |
| TBJE477*006 J □ # @ 0 ^ ++     | TBJE477*006 J □ LC 9 ^ 45 | E | 470                                 | 6.3                                 | 200                                 | 21            | 210           | 420            | 8            | 10           | 12            | 0.165                             | 908                              | 817                              | 363                               | 182                              | 163                              | 73                                |
| TBJU687*006 R □ # @ 0 ^ ++     | TBJU687*006 R □ LC 9 ^ 45 | U | 680                                 | 6.3                                 | 500                                 | 30            | 300           | 600            | 30           | 45           | 45            | 0.165                             | 574                              | 517                              | 230                               | 287                              | 259                              | 115                               |
| TBJU687*006 J □ # @ 0 ^ ++     | TBJU687*006 J □ LC 9 ^ 45 | U | 680                                 | 6.3                                 | 250                                 | 30            | 300           | 600            | 30           | 45           | 45            | 0.165                             | 812                              | 731                              | 325                               | 203                              | 183                              | 81                                |
| TBJA155*010 R □ # @ 0 ^ ++     | TBJA155*010 R □ LC 9 ^ 45 | A | 1.5                                 | 10                                  | 7000                                | 0.3           | 3             | 6              | 6            | 9            | 10            | 0.075                             | 104                              | 93                               | 41                                | 725                              | 652                              | 290                               |
| TBJA225*010 R □ # @ 0 ^ ++     | TBJA225*010 R □ LC 9 ^ 45 | A | 2.2                                 | 10                                  | 7000                                | 0.3           | 3             | 6              | 6            | 9            | 10            | 0.075                             | 104                              | 93                               | 41                                | 725                              | 652                              | 290                               |
| TBJA475*010 R □ # @ 0 ^ ++     | TBJA475*010 R □ LC 9 ^ 45 | A | 4.7                                 | 10                                  | 2900                                | 0.35          | 3.5           | 7              | 6            | 9            | 10            | 0.075                             | 161                              | 145                              | 64                                | 466                              | 420                              | 187                               |
| TBJA475*010 J □ # @ 0 ^ ++     | TBJA475*010 J □ LC 9 ^ 45 | A | 4.7                                 | 10                                  | 2000                                | 0.35          | 3.5           | 7              | 6            | 9            | 10            | 0.075                             | 194                              | 174                              | 77                                | 387                              | 349                              | 155                               |
| TBJA685*010 R □ # @ 0 ^ ++     | TBJA685*010 R □ LC 9 ^ 45 | A | 6.8                                 | 10                                  | 2650                                | 0.51          | 5.1           | 10.2           | 6            | 9            | 10            | 0.075                             | 168                              | 151                              | 67                                | 446                              | 401                              | 178                               |
| TBJA685*010 J □ # @ 0 ^ ++     | TBJA685*010 J □ LC 9 ^ 45 | A | 6.8                                 | 10                                  | 1800                                | 0.51          | 5.1           | 10.2           | 6            | 9            | 10            | 0.075                             | 204                              | 184                              | 82                                | 367                              | 331                              | 147                               |
| TBJB685*010 R □ # @ 0 ^ ++     | TBJB685*010 R □ LC 9 ^ 45 | B | 6.8                                 | 10                                  | 3000                                | 0.51          | 5.1           | 10.2           | 6            | 9            | 10            | 0.085                             | 168                              | 151                              | 67                                | 505                              | 454                              | 202                               |
| TBJA106*010 R □ # @ 0 ^ ++     | TBJA106*010 R □ LC 9 ^ 45 | A | 10                                  | 10                                  | 2200                                | 0.75          | 7.5           | 15             | 6            | 9            | 10            | 0.075                             | 185                              | 166                              | 74                                | 406                              | 366                              | 162                               |
| TBJA106*010 J □ # @ 0 ^ ++     | TBJA106*010 J □ LC 9 ^ 45 | A | 10                                  | 10                                  | 1800                                | 0.75          | 7.5           | 15             | 6            | 9            | 10            | 0.075                             | 204                              | 184                              | 82                                | 367                              | 331                              | 147                               |
| TBJB106*010 R □ # @ 0 ^ ++     | TBJB106*010 R □ LC 9 ^ 45 | B | 10                                  | 10                                  | 2200                                | 0.75          | 7.5           | 15             | 6            | 9            | 10            | 0.085                             | 197                              | 177                              | 79                                | 432                              | 389                              | 173                               |
| TBJB106*010 J □ # @ 0 ^ ++     | TBJB106*010 J □ LC 9 ^ 45 | B | 10                                  | 10                                  | 800                                 | 0.75          | 7.5           | 15             | 6            | 9            | 10            | 0.085                             | 326                              | 293                              | 130                               | 261                              | 235                              | 104                               |
| TBJA156*010 R □ # @ 0 ^ ++     | TBJA156*010 R □ LC 9 ^ 45 | A | 15                                  | 10                                  | 1800                                | 1.1           | 11            | 22             | 6            | 9            | 10            | 0.075                             | 204                              | 184                              | 82                                | 367                              | 331                              | 147                               |
| TBJA156*010 J □ # @ 0 ^ ++     | TBJA156*010 J □ LC 9 ^ 45 | A | 15                                  | 10                                  | 1000                                | 1.1           | 11            | 22             | 6            | 9            | 10            | 0.075                             | 274                              | 246                              | 110                               | 274                              | 246                              | 110                               |
| TBJB156*010 R □ # @ 0 ^ ++     | TBJB156*010 R □ LC 9 ^ 45 | B | 15                                  | 10                                  | 2030                                | 1.1           | 11            | 22             | 6            | 9            | 10            | 0.085                             | 205                              | 184                              | 82                                | 415                              | 374                              | 166                               |
| TBJB156*010 J □ # @ 0 ^ ++     | TBJB156*010 J □ LC 9 ^ 45 | B | 15                                  | 10                                  | 600                                 | 1.1           | 11            | 22             | 6            | 9            | 10            | 0.085                             | 376                              | 339                              | 151                               | 226                              | 203                              | 90                                |
| TBJC156*010 R □ # @ 0 ^ ++     | TBJC156*010 R □ LC 9 ^ 45 | C | 15                                  | 10                                  | 2000                                | 1.1           | 11            | 22             | 6            | 9            | 10            | 0.110                             | 235                              | 211                              | 94                                | 469                              | 422                              | 188                               |
| TBJB226*010 R □ # @ 0 ^ ++     | TBJB226*010 R □ LC 9 ^ 45 | B | 22                                  | 10                                  | 1880                                | 1.7           | 17            | 34             | 6            | 9            | 10            | 0.085                             | 213                              | 191                              | 85                                | 400                              | 360                              | 160                               |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus – SRC9000 Space Level



| RATING & PART NUMBER REFERENCE |                           |      | Parametric Specifications by Rating |                                     |                                     |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                  |                                  |                                   |                                  |                                  |                                   |
|--------------------------------|---------------------------|------|-------------------------------------|-------------------------------------|-------------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|----------------------------------|----------------------------------|-----------------------------------|----------------------------------|----------------------------------|-----------------------------------|
|                                |                           |      | Cap<br>@ 120Hz<br>µF<br>@ 25°C      | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>mOhms<br>@ +25°C | DCL max       |               |                | DF Max       |                  |              | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>mA<br>(100kHz) | 85°C<br>Ripple<br>mA<br>(100kHz) | 125°C<br>Ripple<br>mA<br>(100kHz) | 25°C<br>Ripple<br>mV<br>(100kHz) | 85°C<br>Ripple<br>mV<br>(100kHz) | 125°C<br>Ripple<br>mV<br>(100kHz) |
|                                |                           |      |                                     |                                     |                                     | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                  |                                  |                                   |                                  |                                  |                                   |
| AVX P/N                        | AVX SRC9000 P/N           | Case |                                     |                                     |                                     |               |               |                |              |                  |              |                                   |                                  |                                  |                                   |                                  |                                  |                                   |
| TBJB226*010 J □ # @ 0 ^ ++     | TBJB226*010 J □ LC 9 ^ 45 | B    | 22                                  | 10                                  | 700                                 | 1.7           | 17            | 34             | 6            | 9                | 10           | 0.085                             | 348                              | 314                              | 139                               | 244                              | 220                              | 98                                |
| TBJB336*010 R □ # @ 0 ^ ++     | TBJB336*010 R □ LC 9 ^ 45 | B    | 33                                  | 10                                  | 1000                                | 2.5           | 25            | 50             | 6            | 9                | 10           | 0.085                             | 292                              | 262                              | 117                               | 292                              | 262                              | 117                               |
| TBJB336*010 J □ # @ 0 ^ ++     | TBJB336*010 J □ LC 9 ^ 45 | B    | 33                                  | 10                                  | 650                                 | 2.5           | 25            | 50             | 6            | 9                | 10           | 0.085                             | 362                              | 325                              | 145                               | 235                              | 212                              | 94                                |
| TBJC336*010 R □ # @ 0 ^ ++     | TBJC336*010 R □ LC 9 ^ 45 | C    | 33                                  | 10                                  | 590                                 | 2.5           | 25            | 50             | 6            | 9                | 10           | 0.110                             | 432                              | 389                              | 173                               | 255                              | 229                              | 102                               |
| TBJC336*010 J □ # @ 0 ^ ++     | TBJC336*010 J □ LC 9 ^ 45 | C    | 33                                  | 10                                  | 300                                 | 2.5           | 25            | 50             | 6            | 9                | 10           | 0.110                             | 606                              | 545                              | 242                               | 182                              | 163                              | 73                                |
| TBJD336*010 R □ # @ 0 ^ ++     | TBJD336*010 R □ LC 9 ^ 45 | D    | 33                                  | 10                                  | 1100                                | 2.5           | 25            | 50             | 6            | 9                | 10           | 0.150                             | 369                              | 332                              | 148                               | 406                              | 366                              | 162                               |
| TBJD336*010 J □ # @ 0 ^ ++     | TBJD336*010 J □ LC 9 ^ 45 | D    | 33                                  | 10                                  | 1100                                | 2.5           | 25            | 50             | 6            | 9                | 10           | 0.150                             | 369                              | 332                              | 148                               | 406                              | 366                              | 162                               |
| TBJC476*010 R □ # @ 0 ^ ++     | TBJC476*010 R □ LC 9 ^ 45 | C    | 47                                  | 10                                  | 540                                 | 3.5           | 35            | 70             | 6            | 9                | 10           | 0.110                             | 451                              | 406                              | 181                               | 244                              | 219                              | 97                                |
| TBJC476*010 J □ # @ 0 ^ ++     | TBJC476*010 J □ LC 9 ^ 45 | C    | 47                                  | 10                                  | 300                                 | 3.5           | 35            | 70             | 6            | 9                | 10           | 0.110                             | 606                              | 545                              | 242                               | 182                              | 163                              | 73                                |
| TBJD476*010 R □ # @ 0 ^ ++     | TBJD476*010 R □ LC 9 ^ 45 | D    | 47                                  | 10                                  | 400                                 | 3.5           | 35            | 70             | 6            | 9                | 10           | 0.150                             | 612                              | 551                              | 245                               | 245                              | 220                              | 98                                |
| TBJD476*010 J □ # @ 0 ^ ++     | TBJD476*010 J □ LC 9 ^ 45 | D    | 47                                  | 10                                  | 400                                 | 3.5           | 35            | 70             | 6            | 9                | 10           | 0.150                             | 612                              | 551                              | 245                               | 245                              | 220                              | 98                                |
| TBJC686*010 R □ # @ 0 ^ ++     | TBJC686*010 R □ LC 9 ^ 45 | C    | 68                                  | 10                                  | 490                                 | 5.1           | 51            | 102            | 6            | 9                | 10           | 0.110                             | 474                              | 426                              | 190                               | 232                              | 209                              | 93                                |
| TBJC686*010 J □ # @ 0 ^ ++     | TBJC686*010 J □ LC 9 ^ 45 | C    | 68                                  | 10                                  | 300                                 | 5.1           | 51            | 102            | 6            | 9                | 10           | 0.110                             | 606                              | 545                              | 242                               | 182                              | 163                              | 73                                |
| TBJC107*010 R □ # @ 0 ^ ++     | TBJC107*010 R □ LC 9 ^ 45 | C    | 100                                 | 10                                  | 500                                 | 7.5           | 75            | 150            | 8            | 10               | 12           | 0.110                             | 469                              | 422                              | 188                               | 235                              | 211                              | 94                                |
| TBJC107*010 J □ # @ 0 ^ ++     | TBJC107*010 J □ LC 9 ^ 45 | C    | 100                                 | 10                                  | 200                                 | 7.5           | 75            | 150            | 8            | 10               | 12           | 0.110                             | 742                              | 667                              | 297                               | 148                              | 133                              | 59                                |
| TBJD107*010 R □ # @ 0 ^ ++     | TBJD107*010 R □ LC 9 ^ 45 | D    | 100                                 | 10                                  | 440                                 | 7.5           | 75            | 150            | 6            | 9                | 10           | 0.150                             | 584                              | 525                              | 234                               | 257                              | 231                              | 103                               |
| TBJD107*010 J □ # @ 0 ^ ++     | TBJD107*010 J □ LC 9 ^ 45 | D    | 100                                 | 10                                  | 150                                 | 7.5           | 75            | 150            | 6            | 9                | 10           | 0.150                             | 1000                             | 900                              | 400                               | 150                              | 135                              | 60                                |
| TBJE107*010 R □ # @ 0 ^ ++     | TBJE107*010 R □ LC 9 ^ 45 | E    | 100                                 | 10                                  | 440                                 | 7.5           | 75            | 150            | 6            | 9                | 10           | 0.165                             | 612                              | 551                              | 245                               | 269                              | 242                              | 108                               |
| TBJE107*010 J □ # @ 0 ^ ++     | TBJE107*010 J □ LC 9 ^ 45 | E    | 100                                 | 10                                  | 100                                 | 7.5           | 75            | 150            | 6            | 9                | 10           | 0.165                             | 1285                             | 1156                             | 514                               | 128                              | 116                              | 51                                |
| TBJD157*010 R □ # @ 0 ^ ++     | TBJD157*010 R □ LC 9 ^ 45 | D    | 150                                 | 10                                  | 400                                 | 11            | 110           | 220            | 8            | 10               | 12           | 0.150                             | 612                              | 551                              | 245                               | 245                              | 220                              | 98                                |
| TBJD157*010 J □ # @ 0 ^ ++     | TBJD157*010 J □ LC 9 ^ 45 | D    | 150                                 | 10                                  | 150                                 | 11            | 110           | 220            | 8            | 10               | 12           | 0.150                             | 1000                             | 900                              | 400                               | 150                              | 135                              | 60                                |
| TBJE157*010 R □ # @ 0 ^ ++     | TBJE157*010 R □ LC 9 ^ 45 | E    | 150                                 | 10                                  | 400                                 | 11            | 110           | 220            | 8            | 10               | 12           | 0.165                             | 642                              | 578                              | 257                               | 257                              | 231                              | 103                               |
| TBJE157*010 J □ # @ 0 ^ ++     | TBJE157*010 J □ LC 9 ^ 45 | E    | 150                                 | 10                                  | 150                                 | 11            | 110           | 220            | 8            | 10               | 12           | 0.165                             | 1049                             | 944                              | 420                               | 157                              | 142                              | 63                                |
| TBJD227*010 R □ # @ 0 ^ ++     | TBJD227*010 R □ LC 9 ^ 45 | D    | 220                                 | 10                                  | 500                                 | 17            | 170           | 340            | 8            | 10               | 12           | 0.150                             | 548                              | 493                              | 219                               | 274                              | 246                              | 110                               |
| TBJE227*010 R □ # @ 0 ^ ++     | TBJE227*010 R □ LC 9 ^ 45 | E    | 220                                 | 10                                  | 360                                 | 17            | 170           | 340            | 8            | 10               | 12           | 0.165                             | 677                              | 609                              | 271                               | 244                              | 219                              | 97                                |
| TBJE227*010 J □ # @ 0 ^ ++     | TBJE227*010 J □ LC 9 ^ 45 | E    | 220                                 | 10                                  | 150                                 | 17            | 170           | 340            | 8            | 10               | 12           | 0.165                             | 1049                             | 944                              | 420                               | 157                              | 142                              | 63                                |
| TBJE337*010 R □ # @ 0 ^ ++     | TBJE337*010 R □ LC 9 ^ 45 | E    | 330                                 | 10                                  | 300                                 | 25            | 250           | 500            | 8            | 10               | 12           | 0.165                             | 742                              | 667                              | 297                               | 222                              | 200                              | 89                                |
| TBJE337*010 J □ # @ 0 ^ ++     | TBJE337*010 J □ LC 9 ^ 45 | E    | 330                                 | 10                                  | 100                                 | 25            | 250           | 500            | 8            | 10               | 12           | 0.165                             | 1285                             | 1156                             | 514                               | 128                              | 116                              | 51                                |
| TBJU477*010 R □ # @ 0 ^ ++     | TBJU477*010 R □ LC 9 ^ 45 | U    | 470                                 | 10                                  | 400                                 | 35            | 350           | 700            | 30           | 45               | 45           | 0.165                             | 642                              | 578                              | 257                               | 257                              | 231                              | 103                               |
| TBJU477*010 J □ # @ 0 ^ ++     | TBJU477*010 J □ LC 9 ^ 45 | U    | 470                                 | 10                                  | 200                                 | 35            | 350           | 700            | 30           | 45               | 45           | 0.165                             | 908                              | 817                              | 363                               | 182                              | 163                              | 73                                |
| TBJA105*016 R □ # @ 0 ^ ++     | TBJA105*016 R □ LC 9 ^ 45 | A    | 1                                   | 16                                  | 10000                               | 0.3           | 3             | 6              | 6            | 9                | 10           | 0.075                             | 87                               | 78                               | 35                                | 866                              | 779                              | 346                               |
| TBJA225*016 R □ # @ 0 ^ ++     | TBJA225*016 R □ LC 9 ^ 45 | A    | 2.2                                 | 16                                  | 4550                                | 0.3           | 3             | 6              | 6            | 9                | 10           | 0.075                             | 128                              | 116                              | 51                                | 584                              | 526                              | 234                               |
| TBJA225*016 J □ # @ 0 ^ ++     | TBJA225*016 J □ LC 9 ^ 45 | A    | 2.2                                 | 16                                  | 3500                                | 0.3           | 3             | 6              | 6            | 9                | 10           | 0.075                             | 146                              | 132                              | 59                                | 512                              | 461                              | 205                               |
| TBJA335*016 R □ # @ 0 ^ ++     | TBJA335*016 R □ LC 9 ^ 45 | A    | 3.3                                 | 16                                  | 3740                                | 0.4           | 4             | 8              | 6            | 9                | 10           | 0.075                             | 142                              | 127                              | 57                                | 530                              | 477                              | 212                               |
| TBJA335*016 J □ # @ 0 ^ ++     | TBJA335*016 J □ LC 9 ^ 45 | A    | 3.3                                 | 16                                  | 3500                                | 0.4           | 4             | 8              | 6            | 9                | 10           | 0.075                             | 146                              | 132                              | 59                                | 512                              | 461                              | 205                               |
| TBJB335*016 R □ # @ 0 ^ ++     | TBJB335*016 R □ LC 9 ^ 45 | B    | 3.3                                 | 16                                  | 4500                                | 0.4           | 4             | 8              | 6            | 9                | 10           | 0.085                             | 137                              | 124                              | 55                                | 618                              | 557                              | 247                               |
| TBJA475*016 R □ # @ 0 ^ ++     | TBJA475*016 R □ LC 9 ^ 45 | A    | 4.7                                 | 16                                  | 3160                                | 0.56          | 5.6           | 11.2           | 6            | 9                | 10           | 0.075                             | 154                              | 139                              | 62                                | 487                              | 438                              | 195                               |
| TBJA475*016 J □ # @ 0 ^ ++     | TBJA475*016 J □ LC 9 ^ 45 | A    | 4.7                                 | 16                                  | 2000                                | 0.56          | 5.6           | 11.2           | 6            | 9                | 10           | 0.075                             | 194                              | 174                              | 77                                | 387                              | 349                              | 155                               |
| TBJB475*016 R □ # @ 0 ^ ++     | TBJB475*016 R □ LC 9 ^ 45 | B    | 4.7                                 | 16                                  | 3160                                | 0.56          | 5.6           | 11.2           | 6            | 9                | 10           | 0.085                             | 164                              | 148                              | 66                                | 518                              | 466                              | 207                               |
| TBJB475*016 J □ # @ 0 ^ ++     | TBJB475*016 J □ LC 9 ^ 45 | B    | 4.7                                 | 16                                  | 1500                                | 0.56          | 5.6           | 11.2           | 6            | 9                | 10           | 0.085                             | 238                              | 214                              | 95                                | 357                              | 321                              | 143                               |
| TBJA685*016 R □ # @ 0 ^ ++     | TBJA685*016 R □ LC 9 ^ 45 | A    | 6.8                                 | 16                                  | 2000                                | 0.82          | 8.2           | 16.4           | 4            | 6                | 8            | 0.075                             | 194                              | 174                              | 77                                | 387                              | 349                              | 155                               |
| TBJA685*016 J □ # @ 0 ^ ++     | TBJA685*016 J □ LC 9 ^ 45 | A    | 6.8                                 | 16                                  | 1500                                | 0.82          | 8.2           | 16.4           | 4            | 6                | 8            | 0.075                             | 224                              | 201                              | 89                                | 335                              | 302                              | 134                               |
| TBJB685*016 R □ # @ 0 ^ ++     | TBJB685*016 R □ LC 9 ^ 45 | B    | 6.8                                 | 16                                  | 2650                                | 0.82          | 8.2           | 16.4           | 6            | 9                | 10           | 0.085                             | 179                              | 161                              | 72                                | 475                              | 427                              | 190                               |
| TBJB685*016 J □ # @ 0 ^ ++     | TBJB685*016 J □ LC 9 ^ 45 | B    | 6.8                                 | 16                                  | 1200                                | 0.82          | 8.2           | 16.4           | 6            | 9                | 10           | 0.085                             | 266                              | 240                              | 106                               | 319                              | 287                              | 128                               |
| TBJC685*016 R □ # @ 0 ^ ++     | TBJC685*016 R □ LC 9 ^ 45 | C    | 6.8                                 | 16                                  | 2500                                | 0.82          | 8.2           | 16.4           | 6            | 9                | 10           | 0.110                             | 210                              | 189                              | 84                                | 524                              | 472                              | 210                               |
| TBJB106*016 R □ # @ 0 ^ ++     | TBJB106*016 R □ LC 9 ^ 45 | B    | 10                                  | 16                                  | 2200                                | 1.2           | 12            | 24             | 6            | 9                | 10           | 0.085                             | 197                              | 177                              | 79                                | 432                              | 389                              | 173                               |
| TBJB106*016 J □ # @ 0 ^ ++     | TBJB106*016 J □ LC 9 ^ 45 | B    | 10                                  | 16                                  | 800                                 | 1.2           | 12            | 24             | 6            | 9                | 10           | 0.085                             | 326                              | 293                              | 130                               | 261                              | 235                              | 104                               |
| TBJC106*016 R □ # @ 0 ^ ++     | TBJC106*016 R □ LC 9 ^ 45 | C    | 10                                  | 16                                  | 2000                                | 1.2           | 12            | 24             | 6            | 9                | 10           | 0.110                             | 235                              | 211                              | 94                                | 469                              | 422                              | 188                               |
| TBJB156*016 R □ # @ 0 ^ ++     | TBJB156*016 R □ LC 9 ^ 45 | B    | 15                                  | 16                                  | 2030                                | 1.8           | 18            | 36             | 6            | 9                | 10           | 0.085                             | 205                              | 184                              | 82                                | 415                              | 374                              | 166                               |
| TBJB156*016 J □ # @ 0 ^ ++     | TBJB156*016 J □ LC 9 ^ 45 | B    | 15                                  | 16                                  | 800                                 | 1.8           | 18            | 36             | 6            | 9                | 10           | 0.085                             | 326                              | 293                              | 130                               | 261                              | 235                              | 104                               |
| TBJB226*016 R □ # @ 0 ^ ++     | TBJB226*016 R □ LC 9 ^ 45 | B    | 22                                  | 16                                  | 1100                                | 2.6           | 26            | 52             | 6            | 9                | 10           | 0.085                             | 278                              | 250                              | 111                               | 306                              | 275                              | 122                               |
| TBJB226*016 J □ # @ 0 ^ ++     | TBJB226*016 J □ LC 9 ^ 45 | B    | 22                                  | 16                                  | 600                                 | 2.6           | 26            | 52             | 6            | 9                | 10           | 0.085                             | 376                              | 339                              | 151                               | 226                              | 203                              | 90                                |
| TBJC226*016 R □ # @ 0 ^ ++     | TBJC226*016 R □ LC 9 ^ 45 | C    | 22                                  | 16                                  | 700                                 | 2.6           | 26            | 52             | 6            | 9                | 10           | 0.110                             | 396                              | 357                              | 159                               | 277                              | 250                              | 111                               |
| TBJC226*016 J □ # @ 0 ^ ++     | TBJC226*016 J □ LC 9 ^ 45 | C    | 22                                  | 16                                  | 350                                 | 2.6           | 26            | 52             | 6            | 9                | 10           | 0.110                             | 561                              | 505                              | 224                               | 196                              | 177                              | 78                                |
| TBJD226*016 R □ # @ 0 ^ ++     | TBJD226*016 R □ LC 9 ^ 45 | D    | 22                                  | 16                                  | 1100                                | 2.6           | 26            | 52             | 6            | 9                | 10           | 0.150                             | 369                              | 332                              | 148                               | 406                              | 366                              | 162                               |
| TBJC336*016 R □ # @ 0 ^ ++     | TBJC336*016 R □ LC 9 ^ 45 | C    | 33                                  | 16                                  | 590                                 | 4             | 40            | 80             | 6            | 9                | 10           | 0.110                             | 432                              | 389                              | 173                               | 255                              | 229                              | 102                               |
| TBJC336*016 J □ # @ 0 ^ ++     | TBJC336*016 J □ LC 9 ^ 45 | C    | 33                                  | 16                                  | 300                                 | 4             | 40            | 80             | 6            | 9                | 10           | 0.110                             | 606                              | 545                              | 242                               | 182                              | 163                              | 73                                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus – SRC9000 Space Level



| RATING & PART NUMBER REFERENCE |                           |      | Parametric Specifications by Rating |                                     |                                     |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                                  |                                  |                                   |                                  |                                  |                                   |
|--------------------------------|---------------------------|------|-------------------------------------|-------------------------------------|-------------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|----------------------------------|----------------------------------|-----------------------------------|----------------------------------|----------------------------------|-----------------------------------|
|                                |                           |      | Cap<br>@ 120Hz<br>µF<br>@ 25°C      | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>mOhms<br>@ +25°C | DCL max       |               |                | DF Max       |                  |              | Power<br>Dissipation<br>W         | 25°C<br>Ripple<br>mA<br>(100kHz) | 85°C<br>Ripple<br>mA<br>(100kHz) | 125°C<br>Ripple<br>mA<br>(100kHz) | 25°C<br>Ripple<br>mV<br>(100kHz) | 85°C<br>Ripple<br>mV<br>(100kHz) | 125°C<br>Ripple<br>mV<br>(100kHz) |
|                                |                           |      |                                     |                                     |                                     | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                                  |                                  |                                   |                                  |                                  |                                   |
| AVX P/N                        | AVX SRC9000 P/N           | Case |                                     |                                     |                                     |               |               |                |              |                  |              |                                   |                                  |                                  |                                   |                                  |                                  |                                   |
| TBJC476*016 R □ # @ 0 ^ ++     | TBJC476*016 R □ LC 9 ^ 45 | C    | 47                                  | 16                                  | 540                                 | 5.6           | 56            | 112            | 6            | 9                | 10           | 0.110                             | 451                              | 406                              | 181                               | 244                              | 219                              | 97                                |
| TBJC476*016 J □ # @ 0 ^ ++     | TBJC476*016 J □ LC 9 ^ 45 | C    | 47                                  | 16                                  | 350                                 | 5.6           | 56            | 112            | 6            | 9                | 10           | 0.110                             | 561                              | 505                              | 224                               | 196                              | 177                              | 78                                |
| TBJD476*016 R □ # @ 0 ^ ++     | TBJD476*016 R □ LC 9 ^ 45 | D    | 47                                  | 16                                  | 540                                 | 5.6           | 56            | 112            | 6            | 9                | 10           | 0.150                             | 527                              | 474                              | 211                               | 285                              | 256                              | 114                               |
| TBJD476*016 J □ # @ 0 ^ ++     | TBJD476*016 J □ LC 9 ^ 45 | D    | 47                                  | 16                                  | 200                                 | 5.6           | 56            | 112            | 6            | 9                | 10           | 0.150                             | 866                              | 779                              | 346                               | 173                              | 156                              | 69                                |
| TBJD686*016 R □ # @ 0 ^ ++     | TBJD686*016 R □ LC 9 ^ 45 | D    | 68                                  | 16                                  | 490                                 | 8.2           | 82            | 164            | 6            | 9                | 10           | 0.150                             | 553                              | 498                              | 221                               | 271                              | 244                              | 108                               |
| TBJD686*016 J □ # @ 0 ^ ++     | TBJD686*016 J □ LC 9 ^ 45 | D    | 68                                  | 16                                  | 150                                 | 8.2           | 82            | 164            | 6            | 9                | 10           | 0.150                             | 1000                             | 900                              | 400                               | 150                              | 135                              | 60                                |
| TBJD107*016 R □ # @ 0 ^ ++     | TBJD107*016 R □ LC 9 ^ 45 | D    | 100                                 | 16                                  | 440                                 | 12            | 120           | 240            | 6            | 9                | 10           | 0.150                             | 584                              | 525                              | 234                               | 257                              | 231                              | 103                               |
| TBJD107*016 J □ # @ 0 ^ ++     | TBJD107*016 J □ LC 9 ^ 45 | D    | 100                                 | 16                                  | 150                                 | 12            | 120           | 240            | 6            | 9                | 10           | 0.150                             | 1000                             | 900                              | 400                               | 150                              | 135                              | 60                                |
| TBJE107*016 R □ # @ 0 ^ ++     | TBJE107*016 R □ LC 9 ^ 45 | E    | 100                                 | 16                                  | 440                                 | 12            | 120           | 240            | 6            | 9                | 10           | 0.165                             | 612                              | 551                              | 245                               | 269                              | 242                              | 108                               |
| TBJE107*016 J □ # @ 0 ^ ++     | TBJE107*016 J □ LC 9 ^ 45 | E    | 100                                 | 16                                  | 150                                 | 12            | 120           | 240            | 6            | 9                | 10           | 0.165                             | 1049                             | 944                              | 420                               | 157                              | 142                              | 63                                |
| TBJE157*016 R □ # @ 0 ^ ++     | TBJE157*016 R □ LC 9 ^ 45 | E    | 150                                 | 16                                  | 300                                 | 16            | 160           | 320            | 6            | 9                | 10           | 0.165                             | 742                              | 667                              | 297                               | 222                              | 200                              | 89                                |
| TBJE157*016 J □ # @ 0 ^ ++     | TBJE157*016 J □ LC 9 ^ 45 | E    | 150                                 | 16                                  | 150                                 | 16            | 160           | 320            | 6            | 9                | 10           | 0.165                             | 1049                             | 944                              | 420                               | 157                              | 142                              | 63                                |
| TBJU227*016 R □ # @ 0 ^ ++     | TBJU227*016 R □ LC 9 ^ 45 | U    | 220                                 | 16                                  | 500                                 | 26.4          | 264           | 528            | 12           | 15               | 15           | 0.165                             | 574                              | 517                              | 230                               | 287                              | 259                              | 115                               |
| TBJU227*016 J □ # @ 0 ^ ++     | TBJU227*016 J □ LC 9 ^ 45 | U    | 220                                 | 16                                  | 200                                 | 26.4          | 264           | 528            | 12           | 15               | 15           | 0.165                             | 908                              | 817                              | 363                               | 182                              | 163                              | 73                                |
| TBJU337*016 R □ # @ 0 ^ ++     | TBJU337*016 R □ LC 9 ^ 45 | U    | 330                                 | 16                                  | 400                                 | 39            | 390           | 780            | 30           | 45               | 45           | 0.165                             | 642                              | 578                              | 257                               | 257                              | 231                              | 103                               |
| TBJU337*016 J □ # @ 0 ^ ++     | TBJU337*016 J □ LC 9 ^ 45 | U    | 330                                 | 16                                  | 200                                 | 39            | 390           | 780            | 30           | 45               | 45           | 0.165                             | 908                              | 817                              | 363                               | 182                              | 163                              | 73                                |
| TBJA105*020 R □ # @ 0 ^ ++     | TBJA105*020 R □ LC 9 ^ 45 | A    | 1                                   | 20                                  | 6630                                | 0.3           | 3             | 6              | 4            | 6                | 8            | 0.075                             | 106                              | 96                               | 43                                | 705                              | 635                              | 282                               |
| TBJA105*020 J □ # @ 0 ^ ++     | TBJA105*020 J □ LC 9 ^ 45 | A    | 1                                   | 20                                  | 3000                                | 0.3           | 3             | 6              | 4            | 6                | 8            | 0.075                             | 158                              | 142                              | 63                                | 474                              | 427                              | 190                               |
| TBJA155*020 R □ # @ 0 ^ ++     | TBJA155*020 R □ LC 9 ^ 45 | A    | 1.5                                 | 20                                  | 5460                                | 0.3           | 3             | 6              | 6            | 9                | 10           | 0.075                             | 117                              | 105                              | 47                                | 640                              | 576                              | 256                               |
| TBJA155*020 J □ # @ 0 ^ ++     | TBJA155*020 J □ LC 9 ^ 45 | A    | 1.5                                 | 20                                  | 3000                                | 0.3           | 3             | 6              | 6            | 9                | 10           | 0.075                             | 158                              | 142                              | 63                                | 474                              | 427                              | 190                               |
| TBJA225*020 R □ # @ 0 ^ ++     | TBJA225*020 R □ LC 9 ^ 45 | A    | 2.2                                 | 20                                  | 4550                                | 0.33          | 3.3           | 6.6            | 6            | 9                | 10           | 0.075                             | 128                              | 116                              | 51                                | 584                              | 526                              | 234                               |
| TBJA225*020 J □ # @ 0 ^ ++     | TBJA225*020 J □ LC 9 ^ 45 | A    | 2.2                                 | 20                                  | 3000                                | 0.33          | 3.3           | 6.6            | 6            | 9                | 10           | 0.075                             | 158                              | 142                              | 63                                | 474                              | 427                              | 190                               |
| TBJA335*020 R □ # @ 0 ^ ++     | TBJA335*020 R □ LC 9 ^ 45 | A    | 3.3                                 | 20                                  | 3740                                | 0.5           | 5             | 10             | 6            | 9                | 10           | 0.075                             | 142                              | 127                              | 57                                | 530                              | 477                              | 212                               |
| TBJA335*020 J □ # @ 0 ^ ++     | TBJA335*020 J □ LC 9 ^ 45 | A    | 3.3                                 | 20                                  | 2500                                | 0.5           | 5             | 10             | 6            | 9                | 10           | 0.075                             | 173                              | 156                              | 69                                | 433                              | 390                              | 173                               |
| TBJB335*020 R □ # @ 0 ^ ++     | TBJB335*020 R □ LC 9 ^ 45 | B    | 3.3                                 | 20                                  | 3740                                | 0.5           | 5             | 10             | 6            | 9                | 10           | 0.085                             | 151                              | 136                              | 60                                | 564                              | 507                              | 226                               |
| TBJB335*020 J □ # @ 0 ^ ++     | TBJB335*020 J □ LC 9 ^ 45 | B    | 3.3                                 | 20                                  | 1300                                | 0.5           | 5             | 10             | 6            | 9                | 10           | 0.085                             | 256                              | 230                              | 102                               | 332                              | 299                              | 133                               |
| TBJA475*020 R □ # @ 0 ^ ++     | TBJA475*020 R □ LC 9 ^ 45 | A    | 4.7                                 | 20                                  | 2500                                | 0.71          | 7.1           | 14.2           | 5            | 8                | 10           | 0.075                             | 173                              | 156                              | 69                                | 433                              | 390                              | 173                               |
| TBJA475*020 J □ # @ 0 ^ ++     | TBJA475*020 J □ LC 9 ^ 45 | A    | 4.7                                 | 20                                  | 1800                                | 0.71          | 7.1           | 14.2           | 5            | 8                | 10           | 0.075                             | 204                              | 184                              | 82                                | 367                              | 331                              | 147                               |
| TBJB475*020 R □ # @ 0 ^ ++     | TBJB475*020 R □ LC 9 ^ 45 | B    | 4.7                                 | 20                                  | 3160                                | 0.71          | 7.1           | 14.2           | 6            | 9                | 10           | 0.085                             | 164                              | 148                              | 66                                | 518                              | 466                              | 207                               |
| TBJB475*020 J □ # @ 0 ^ ++     | TBJB475*020 J □ LC 9 ^ 45 | B    | 4.7                                 | 20                                  | 1000                                | 0.71          | 7.1           | 14.2           | 6            | 9                | 10           | 0.085                             | 292                              | 262                              | 117                               | 292                              | 262                              | 117                               |
| TBJB685*020 R □ # @ 0 ^ ++     | TBJB685*020 R □ LC 9 ^ 45 | B    | 6.8                                 | 20                                  | 2650                                | 1             | 10            | 20             | 6            | 9                | 10           | 0.085                             | 179                              | 161                              | 72                                | 475                              | 427                              | 190                               |
| TBJB685*020 J □ # @ 0 ^ ++     | TBJB685*020 J □ LC 9 ^ 45 | B    | 6.8                                 | 20                                  | 1000                                | 1             | 10            | 20             | 6            | 9                | 10           | 0.085                             | 292                              | 262                              | 117                               | 292                              | 262                              | 117                               |
| TBJC685*020 R □ # @ 0 ^ ++     | TBJC685*020 R □ LC 9 ^ 45 | C    | 6.8                                 | 20                                  | 2000                                | 1             | 10            | 20             | 6            | 9                | 10           | 0.110                             | 235                              | 211                              | 94                                | 469                              | 422                              | 188                               |
| TBJB106*020 R □ # @ 0 ^ ++     | TBJB106*020 R □ LC 9 ^ 45 | B    | 10                                  | 20                                  | 2200                                | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.085                             | 197                              | 177                              | 79                                | 432                              | 389                              | 173                               |
| TBJB106*020 J □ # @ 0 ^ ++     | TBJB106*020 J □ LC 9 ^ 45 | B    | 10                                  | 20                                  | 1000                                | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.085                             | 292                              | 262                              | 117                               | 292                              | 262                              | 117                               |
| TBJC106*020 R □ # @ 0 ^ ++     | TBJC106*020 R □ LC 9 ^ 45 | C    | 10                                  | 20                                  | 800                                 | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.110                             | 371                              | 334                              | 148                               | 297                              | 267                              | 119                               |
| TBJC106*020 J □ # @ 0 ^ ++     | TBJC106*020 J □ LC 9 ^ 45 | C    | 10                                  | 20                                  | 500                                 | 1.5           | 15            | 30             | 6            | 9                | 10           | 0.110                             | 469                              | 422                              | 188                               | 235                              | 211                              | 94                                |
| TBJB156*020 R □ # @ 0 ^ ++     | TBJB156*020 R □ LC 9 ^ 45 | B    | 15                                  | 20                                  | 1400                                | 2.3           | 23            | 46             | 6            | 9                | 10           | 0.085                             | 246                              | 222                              | 99                                | 345                              | 310                              | 138                               |
| TBJB156*020 J □ # @ 0 ^ ++     | TBJB156*020 J □ LC 9 ^ 45 | B    | 15                                  | 20                                  | 500                                 | 2.3           | 23            | 46             | 6            | 9                | 10           | 0.085                             | 412                              | 371                              | 165                               | 206                              | 186                              | 82                                |
| TBJC156*020 R □ # @ 0 ^ ++     | TBJC156*020 R □ LC 9 ^ 45 | C    | 15                                  | 20                                  | 720                                 | 2.3           | 23            | 46             | 6            | 9                | 10           | 0.110                             | 391                              | 352                              | 156                               | 281                              | 253                              | 113                               |
| TBJC156*020 J □ # @ 0 ^ ++     | TBJC156*020 J □ LC 9 ^ 45 | C    | 15                                  | 20                                  | 400                                 | 2.3           | 23            | 46             | 6            | 9                | 10           | 0.110                             | 524                              | 472                              | 210                               | 210                              | 189                              | 84                                |
| TBJD156*020 R □ # @ 0 ^ ++     | TBJD156*020 R □ LC 9 ^ 45 | D    | 15                                  | 20                                  | 1100                                | 2.3           | 23            | 46             | 6            | 9                | 10           | 0.150                             | 369                              | 332                              | 148                               | 406                              | 366                              | 162                               |
| TBJC226*020 R □ # @ 0 ^ ++     | TBJC226*020 R □ LC 9 ^ 45 | C    | 22                                  | 20                                  | 650                                 | 3.3           | 33            | 66             | 6            | 9                | 10           | 0.110                             | 411                              | 370                              | 165                               | 267                              | 241                              | 107                               |
| TBJC226*020 J □ # @ 0 ^ ++     | TBJC226*020 J □ LC 9 ^ 45 | C    | 22                                  | 20                                  | 400                                 | 3.3           | 33            | 66             | 6            | 9                | 10           | 0.110                             | 524                              | 472                              | 210                               | 210                              | 189                              | 84                                |
| TBJD226*020 R □ # @ 0 ^ ++     | TBJD226*020 R □ LC 9 ^ 45 | D    | 22                                  | 20                                  | 650                                 | 3.3           | 33            | 66             | 6            | 9                | 10           | 0.150                             | 480                              | 432                              | 192                               | 312                              | 281                              | 125                               |
| TBJD226*020 J □ # @ 0 ^ ++     | TBJD226*020 J □ LC 9 ^ 45 | D    | 22                                  | 20                                  | 150                                 | 3.3           | 33            | 66             | 6            | 9                | 10           | 0.150                             | 1000                             | 900                              | 400                               | 150                              | 135                              | 60                                |
| TBJC336*020 R □ # @ 0 ^ ++     | TBJC336*020 R □ LC 9 ^ 45 | C    | 33                                  | 20                                  | 590                                 | 5             | 50            | 100            | 6            | 9                | 10           | 0.110                             | 432                              | 389                              | 173                               | 255                              | 229                              | 102                               |
| TBJC336*020 J □ # @ 0 ^ ++     | TBJC336*020 J □ LC 9 ^ 45 | C    | 33                                  | 20                                  | 300                                 | 5             | 50            | 100            | 6            | 9                | 10           | 0.110                             | 606                              | 545                              | 242                               | 182                              | 163                              | 73                                |
| TBJD336*020 R □ # @ 0 ^ ++     | TBJD336*020 R □ LC 9 ^ 45 | D    | 33                                  | 20                                  | 590                                 | 5             | 50            | 100            | 6            | 9                | 10           | 0.150                             | 504                              | 454                              | 202                               | 297                              | 268                              | 119                               |
| TBJD336*020 J □ # @ 0 ^ ++     | TBJD336*020 J □ LC 9 ^ 45 | D    | 33                                  | 20                                  | 250                                 | 5             | 50            | 100            | 6            | 9                | 10           | 0.150                             | 775                              | 697                              | 310                               | 194                              | 174                              | 77                                |
| TBJD476*020 R □ # @ 0 ^ ++     | TBJD476*020 R □ LC 9 ^ 45 | D    | 47                                  | 20                                  | 540                                 | 7.1           | 71            | 142            | 6            | 9                | 10           | 0.150                             | 527                              | 474                              | 211                               | 285                              | 256                              | 114                               |
| TBJD476*020 J □ # @ 0 ^ ++     | TBJD476*020 J □ LC 9 ^ 45 | D    | 47                                  | 20                                  | 200                                 | 7.1           | 71            | 142            | 6            | 9                | 10           | 0.150                             | 866                              | 779                              | 346                               | 173                              | 156                              | 69                                |
| TBJD686*020 R □ # @ 0 ^ ++     | TBJD686*020 R □ LC 9 ^ 45 | D    | 68                                  | 20                                  | 490                                 | 10            | 100           | 200            | 6            | 9                | 10           | 0.150                             | 553                              | 498                              | 221                               | 271                              | 244                              | 108                               |
| TBJD686*020 J □ # @ 0 ^ ++     | TBJD686*020 J □ LC 9 ^ 45 | D    | 68                                  | 20                                  | 200                                 | 10            | 100           | 200            | 6            | 9                | 10           | 0.150                             | 866                              | 779                              | 346                               | 173                              | 156                              | 69                                |
| TBJE686*020 R □ # @ 0 ^ ++     | TBJE686*020 R □ LC 9 ^ 45 | E    | 68                                  | 20                                  | 490                                 | 10            | 100           | 200            | 6            | 9                | 10           | 0.165                             | 580                              | 522                              | 232                               | 284                              | 256                              | 114                               |
| TBJE686*020 J □ # @ 0 ^ ++     | TBJE686*020 J □ LC 9 ^ 45 | E    | 68                                  | 20                                  | 120                                 | 10            | 100           | 200            | 6            | 9                | 10           | 0.165                             | 1173                             | 1055                             | 469                               | 141                              | 127                              | 56                                |
| TBJE107*020 R □ # @ 0 ^ ++     | TBJE107*020 R □ LC 9 ^ 45 | E    | 100                                 | 20                                  | 300                                 | 15            | 150           | 300            | 6            | 9                | 10           | 0.165                             | 742                              | 667                              | 297                               | 222                              | 200                              | 89                                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus – SRC9000 Space Level



| RATING & PART NUMBER REFERENCE |                           |      | Parametric Specifications by Rating |                               |                               |               |               |                |              |                  | Typical RMS Ripple Data by Rating |                            |                            |                             |                            |                            |                             |     |
|--------------------------------|---------------------------|------|-------------------------------------|-------------------------------|-------------------------------|---------------|---------------|----------------|--------------|------------------|-----------------------------------|----------------------------|----------------------------|-----------------------------|----------------------------|----------------------------|-----------------------------|-----|
|                                |                           |      | Cap @ 120Hz<br>µF @ 25°C            | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>mOhms @ +25°C | DCL max       |               |                | DF Max       |                  | Power Dissipation<br>W            | 25°C Ripple<br>mA (100kHz) | 85°C Ripple<br>mA (100kHz) | 125°C Ripple<br>mA (100kHz) | 25°C Ripple<br>mV (100kHz) | 85°C Ripple<br>mV (100kHz) | 125°C Ripple<br>mV (100kHz) |     |
| AVX P/N                        | AVX SRC9000 P/N           | Case |                                     |                               |                               | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%)                      |                            |                            |                             |                            |                            |                             |     |
| TBJE107*020 J □ # @ 0 ^ ++     | TBJE107*020 J □ LC 9 ^ 45 | E    | 100                                 | 20                            | 150                           | 15            | 150           | 300            | 6            | 9                | 10                                | 0.165                      | 1049                       | 944                         | 420                        | 157                        | 142                         | 63  |
| TBJU157*020 R □ # @ 0 ^ ++     | TBJU157*020 R □ LC 9 ^ 45 | U    | 150                                 | 20                            | 500                           | 22            | 220           | 440            | 30           | 45               | 45                                | 0.165                      | 574                        | 517                         | 230                        | 287                        | 259                         | 115 |
| TBJU157*020 J □ # @ 0 ^ ++     | TBJU157*020 J □ LC 9 ^ 45 | U    | 150                                 | 20                            | 250                           | 22            | 220           | 440            | 30           | 45               | 45                                | 0.165                      | 812                        | 731                         | 325                        | 203                        | 183                         | 81  |
| TBJA474*025 R □ # @ 0 ^ ++     | TBJA474*025 R □ LC 9 ^ 45 | A    | 0.47                                | 25                            | 9530                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 89                         | 80                          | 35                         | 845                        | 761                         | 338 |
| TBJA474*025 J □ # @ 0 ^ ++     | TBJA474*025 J □ LC 9 ^ 45 | A    | 0.47                                | 25                            | 7000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 104                        | 93                          | 41                         | 725                        | 652                         | 290 |
| TBJA684*025 R □ # @ 0 ^ ++     | TBJA684*025 R □ LC 9 ^ 45 | A    | 0.68                                | 25                            | 7980                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 97                         | 87                          | 39                         | 774                        | 696                         | 309 |
| TBJA684*025 J □ # @ 0 ^ ++     | TBJA684*025 J □ LC 9 ^ 45 | A    | 0.68                                | 25                            | 6000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 112                        | 101                         | 45                         | 671                        | 604                         | 268 |
| TBJA105*025 R □ # @ 0 ^ ++     | TBJA105*025 R □ LC 9 ^ 45 | A    | 1                                   | 25                            | 6630                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 106                        | 96                          | 43                         | 705                        | 635                         | 282 |
| TBJA105*025 J □ # @ 0 ^ ++     | TBJA105*025 J □ LC 9 ^ 45 | A    | 1                                   | 25                            | 3000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 158                        | 142                         | 63                         | 474                        | 427                         | 190 |
| TBJA155*025 R □ # @ 0 ^ ++     | TBJA155*025 R □ LC 9 ^ 45 | A    | 1.5                                 | 25                            | 5460                          | 0.3           | 3             | 6              | 6            | 9                | 10                                | 0.075                      | 117                        | 105                         | 47                         | 640                        | 576                         | 256 |
| TBJA155*025 J □ # @ 0 ^ ++     | TBJA155*025 J □ LC 9 ^ 45 | A    | 1.5                                 | 25                            | 3000                          | 0.3           | 3             | 6              | 6            | 9                | 10                                | 0.075                      | 158                        | 142                         | 63                         | 474                        | 427                         | 190 |
| TBJB155*025 R □ # @ 0 ^ ++     | TBJB155*025 R □ LC 9 ^ 45 | B    | 1.5                                 | 25                            | 5000                          | 0.3           | 3             | 6              | 6            | 9                | 10                                | 0.085                      | 130                        | 117                         | 52                         | 652                        | 587                         | 261 |
| TBJA225*025 R □ # @ 0 ^ ++     | TBJA225*025 R □ LC 9 ^ 45 | A    | 2.2                                 | 25                            | 2900                          | 0.41          | 4.1           | 8.2            | 6            | 9                | 10                                | 0.075                      | 161                        | 145                         | 64                         | 466                        | 420                         | 187 |
| TBJA225*025 J □ # @ 0 ^ ++     | TBJA225*025 J □ LC 9 ^ 45 | A    | 2.2                                 | 25                            | 1600                          | 0.41          | 4.1           | 8.2            | 6            | 9                | 10                                | 0.075                      | 217                        | 195                         | 87                         | 346                        | 312                         | 139 |
| TBJB225*025 R □ # @ 0 ^ ++     | TBJB225*025 R □ LC 9 ^ 45 | B    | 2.2                                 | 25                            | 4650                          | 0.41          | 4.1           | 8.2            | 6            | 9                | 10                                | 0.085                      | 137                        | 123                         | 55                         | 622                        | 560                         | 249 |
| TBJB225*025 J □ # @ 0 ^ ++     | TBJB225*025 J □ LC 9 ^ 45 | B    | 2.2                                 | 25                            | 1200                          | 0.41          | 4.1           | 8.2            | 6            | 9                | 10                                | 0.085                      | 266                        | 240                         | 106                        | 319                        | 287                         | 128 |
| TBJB335*025 R □ # @ 0 ^ ++     | TBJB335*025 R □ LC 9 ^ 45 | B    | 3.3                                 | 25                            | 3740                          | 0.62          | 6.2           | 12.4           | 6            | 9                | 10                                | 0.085                      | 151                        | 136                         | 60                         | 564                        | 507                         | 226 |
| TBJB335*025 J □ # @ 0 ^ ++     | TBJB335*025 J □ LC 9 ^ 45 | B    | 3.3                                 | 25                            | 2000                          | 0.62          | 6.2           | 12.4           | 6            | 9                | 10                                | 0.085                      | 206                        | 186                         | 82                         | 412                        | 371                         | 165 |
| TBJB475*025 R □ # @ 0 ^ ++     | TBJB475*025 R □ LC 9 ^ 45 | B    | 4.7                                 | 25                            | 3160                          | 0.88          | 8.8           | 17.6           | 6            | 9                | 10                                | 0.085                      | 164                        | 148                         | 66                         | 518                        | 466                         | 207 |
| TBJB475*025 J □ # @ 0 ^ ++     | TBJB475*025 J □ LC 9 ^ 45 | B    | 4.7                                 | 25                            | 1000                          | 0.88          | 8.8           | 17.6           | 6            | 9                | 10                                | 0.085                      | 292                        | 262                         | 117                        | 292                        | 262                         | 117 |
| TBJB685*025 R □ # @ 0 ^ ++     | TBJB685*025 R □ LC 9 ^ 45 | B    | 6.8                                 | 25                            | 1500                          | 1.3           | 13            | 26             | 6            | 9                | 10                                | 0.085                      | 238                        | 214                         | 95                         | 357                        | 321                         | 143 |
| TBJB685*025 J □ # @ 0 ^ ++     | TBJB685*025 J □ LC 9 ^ 45 | B    | 6.8                                 | 25                            | 1000                          | 1.3           | 13            | 26             | 6            | 9                | 10                                | 0.085                      | 292                        | 262                         | 117                        | 292                        | 262                         | 117 |
| TBJC685*025 R □ # @ 0 ^ ++     | TBJC685*025 R □ LC 9 ^ 45 | C    | 6.8                                 | 25                            | 1070                          | 1.3           | 13            | 26             | 6            | 9                | 10                                | 0.110                      | 321                        | 289                         | 128                        | 343                        | 309                         | 137 |
| TBJC685*025 J □ # @ 0 ^ ++     | TBJC685*025 J □ LC 9 ^ 45 | C    | 6.8                                 | 25                            | 600                           | 1.3           | 13            | 26             | 6            | 9                | 10                                | 0.110                      | 428                        | 385                         | 171                        | 257                        | 231                         | 103 |
| TBJC106*025 R □ # @ 0 ^ ++     | TBJC106*025 R □ LC 9 ^ 45 | C    | 10                                  | 25                            | 800                           | 1.9           | 19            | 38             | 6            | 9                | 10                                | 0.110                      | 371                        | 334                         | 148                        | 297                        | 267                         | 119 |
| TBJC106*025 J □ # @ 0 ^ ++     | TBJC106*025 J □ LC 9 ^ 45 | C    | 10                                  | 25                            | 600                           | 1.9           | 19            | 38             | 6            | 9                | 10                                | 0.110                      | 428                        | 385                         | 171                        | 257                        | 231                         | 103 |
| TBJD106*025 R □ # @ 0 ^ ++     | TBJD106*025 R □ LC 9 ^ 45 | D    | 10                                  | 25                            | 1200                          | 1.9           | 19            | 38             | 6            | 9                | 10                                | 0.150                      | 354                        | 318                         | 141                        | 424                        | 382                         | 170 |
| TBJC156*025 R □ # @ 0 ^ ++     | TBJC156*025 R □ LC 9 ^ 45 | C    | 15                                  | 25                            | 720                           | 2.8           | 28            | 56             | 6            | 9                | 10                                | 0.110                      | 391                        | 352                         | 156                        | 281                        | 253                         | 113 |
| TBJC156*025 J □ # @ 0 ^ ++     | TBJC156*025 J □ LC 9 ^ 45 | C    | 15                                  | 25                            | 500                           | 2.8           | 28            | 56             | 6            | 9                | 10                                | 0.110                      | 469                        | 422                         | 188                        | 235                        | 211                         | 94  |
| TBJD156*025 R □ # @ 0 ^ ++     | TBJD156*025 R □ LC 9 ^ 45 | D    | 15                                  | 25                            | 720                           | 2.8           | 28            | 56             | 6            | 9                | 10                                | 0.150                      | 456                        | 411                         | 183                        | 329                        | 296                         | 131 |
| TBJD156*025 J □ # @ 0 ^ ++     | TBJD156*025 J □ LC 9 ^ 45 | D    | 15                                  | 25                            | 300                           | 2.8           | 28            | 56             | 6            | 9                | 10                                | 0.150                      | 707                        | 636                         | 283                        | 212                        | 191                         | 85  |
| TBJD226*025 R □ # @ 0 ^ ++     | TBJD226*025 R □ LC 9 ^ 45 | D    | 22                                  | 25                            | 650                           | 4.1           | 41            | 82             | 6            | 9                | 10                                | 0.150                      | 480                        | 432                         | 192                        | 312                        | 281                         | 125 |
| TBJD226*025 J □ # @ 0 ^ ++     | TBJD226*025 J □ LC 9 ^ 45 | D    | 22                                  | 25                            | 300                           | 4.1           | 41            | 82             | 6            | 9                | 10                                | 0.150                      | 707                        | 636                         | 283                        | 212                        | 191                         | 85  |
| TBJD336*025 R □ # @ 0 ^ ++     | TBJD336*025 R □ LC 9 ^ 45 | D    | 33                                  | 25                            | 590                           | 6.2           | 62            | 124            | 6            | 9                | 10                                | 0.150                      | 504                        | 454                         | 202                        | 297                        | 268                         | 119 |
| TBJD336*025 J □ # @ 0 ^ ++     | TBJD336*025 J □ LC 9 ^ 45 | D    | 33                                  | 25                            | 400                           | 6.2           | 62            | 124            | 6            | 9                | 10                                | 0.150                      | 612                        | 551                         | 245                        | 245                        | 220                         | 98  |
| TBJD476*025 R □ # @ 0 ^ ++     | TBJD476*025 R □ LC 9 ^ 45 | D    | 47                                  | 25                            | 540                           | 8.8           | 88            | 176            | 6            | 9                | 10                                | 0.150                      | 527                        | 474                         | 211                        | 285                        | 256                         | 114 |
| TBJD476*025 J □ # @ 0 ^ ++     | TBJD476*025 J □ LC 9 ^ 45 | D    | 47                                  | 25                            | 250                           | 8.8           | 88            | 176            | 6            | 9                | 10                                | 0.150                      | 775                        | 697                         | 310                        | 194                        | 174                         | 77  |
| TBJE476*025 R □ # @ 0 ^ ++     | TBJE476*025 R □ LC 9 ^ 45 | E    | 47                                  | 25                            | 540                           | 8.8           | 88            | 176            | 6            | 9                | 10                                | 0.165                      | 553                        | 497                         | 221                        | 298                        | 269                         | 119 |
| TBJE476*025 J □ # @ 0 ^ ++     | TBJE476*025 J □ LC 9 ^ 45 | E    | 47                                  | 25                            | 150                           | 8.8           | 88            | 176            | 6            | 9                | 10                                | 0.165                      | 1049                       | 944                         | 420                        | 157                        | 142                         | 63  |
| TBJU686*025 R □ # @ 0 ^ ++     | TBJU686*025 R □ LC 9 ^ 45 | U    | 68                                  | 25                            | 500                           | 12            | 120           | 240            | 30           | 45               | 45                                | 0.165                      | 574                        | 517                         | 230                        | 287                        | 259                         | 115 |
| TBJU107*025 R □ # @ 0 ^ ++     | TBJU107*025 R □ LC 9 ^ 45 | U    | 100                                 | 25                            | 500                           | 18            | 180           | 360            | 30           | 45               | 45                                | 0.165                      | 574                        | 517                         | 230                        | 287                        | 259                         | 115 |
| TBJA104*035 R □ # @ 0 ^ ++     | TBJA104*035 R □ LC 9 ^ 45 | A    | 0.1                                 | 35                            | 20000                         | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 61                         | 55                          | 24                         | 1225                       | 1102                        | 490 |
| TBJA154*035 R □ # @ 0 ^ ++     | TBJA154*035 R □ LC 9 ^ 45 | A    | 0.15                                | 35                            | 16470                         | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 67                         | 61                          | 27                         | 1111                       | 1000                        | 445 |
| TBJA154*035 J □ # @ 0 ^ ++     | TBJA154*035 J □ LC 9 ^ 45 | A    | 0.15                                | 35                            | 6000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 112                        | 101                         | 45                         | 671                        | 604                         | 268 |
| TBJA224*035 R □ # @ 0 ^ ++     | TBJA224*035 R □ LC 9 ^ 45 | A    | 0.22                                | 35                            | 13710                         | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 74                         | 67                          | 30                         | 1014                       | 913                         | 406 |
| TBJA224*035 J □ # @ 0 ^ ++     | TBJA224*035 J □ LC 9 ^ 45 | A    | 0.22                                | 35                            | 6000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 112                        | 101                         | 45                         | 671                        | 604                         | 268 |
| TBJA334*035 R □ # @ 0 ^ ++     | TBJA334*035 R □ LC 9 ^ 45 | A    | 0.33                                | 35                            | 11280                         | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 82                         | 73                          | 33                         | 920                        | 828                         | 368 |
| TBJA334*035 J □ # @ 0 ^ ++     | TBJA334*035 J □ LC 9 ^ 45 | A    | 0.33                                | 35                            | 6000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 112                        | 101                         | 45                         | 671                        | 604                         | 268 |
| TBJA474*035 R □ # @ 0 ^ ++     | TBJA474*035 R □ LC 9 ^ 45 | A    | 0.47                                | 35                            | 9530                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 89                         | 80                          | 35                         | 845                        | 761                         | 338 |
| TBJA474*035 J □ # @ 0 ^ ++     | TBJA474*035 J □ LC 9 ^ 45 | A    | 0.47                                | 35                            | 4000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 137                        | 123                         | 55                         | 548                        | 493                         | 219 |
| TBJA684*035 R □ # @ 0 ^ ++     | TBJA684*035 R □ LC 9 ^ 45 | A    | 0.68                                | 35                            | 7980                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 97                         | 87                          | 39                         | 774                        | 696                         | 309 |
| TBJA684*035 J □ # @ 0 ^ ++     | TBJA684*035 J □ LC 9 ^ 45 | A    | 0.68                                | 35                            | 6000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 112                        | 101                         | 45                         | 671                        | 604                         | 268 |
| TBJA105*035 R □ # @ 0 ^ ++     | TBJA105*035 R □ LC 9 ^ 45 | A    | 1                                   | 35                            | 6630                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 106                        | 96                          | 43                         | 705                        | 635                         | 282 |
| TBJA105*035 J □ # @ 0 ^ ++     | TBJA105*035 J □ LC 9 ^ 45 | A    | 1                                   | 35                            | 3000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 158                        | 142                         | 63                         | 474                        | 427                         | 190 |
| TBJB105*035 R □ # @ 0 ^ ++     | TBJB105*035 R □ LC 9 ^ 45 | B    | 1                                   | 35                            | 3400                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.085                      | 158                        | 142                         | 63                         | 538                        | 484                         | 215 |
| TBJB105*035 J □ # @ 0 ^ ++     | TBJB105*035 J □ LC 9 ^ 45 | B    | 1                                   | 35                            | 2000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.085                      | 206                        | 186                         | 82                         | 412                        | 371                         | 165 |
| TBJA155*035 R □ # @ 0 ^ ++     | TBJA155*035 R □ LC 9 ^ 45 | A    | 1.5                                 | 35                            | 3100                          | 0.39          | 3.9           | 7.8            | 6            | 9                | 10                                | 0.075                      | 156                        | 140                         | 62                         | 482                        | 434                         | 193 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# TBJ Series

## COTS-Plus – SRC9000 Space Level



| RATING & PART NUMBER REFERENCE |                           |      | Parametric Specifications by Rating |                               |                               |               |               |                |              |                  | Typical RMS Ripple Data by Rating |                            |                            |                             |                            |                            |                             |     |
|--------------------------------|---------------------------|------|-------------------------------------|-------------------------------|-------------------------------|---------------|---------------|----------------|--------------|------------------|-----------------------------------|----------------------------|----------------------------|-----------------------------|----------------------------|----------------------------|-----------------------------|-----|
|                                |                           |      | Cap @ 120Hz<br>μF @ 25°C            | DC Rated Voltage @ +85°C<br>V | ESR @ 100kHz<br>mOhms @ +25°C | DCL max       |               |                | DF Max       |                  | Power Dissipation<br>W            | 25°C Ripple<br>mA (100kHz) | 85°C Ripple<br>mA (100kHz) | 125°C Ripple<br>mA (100kHz) | 25°C Ripple<br>mV (100kHz) | 85°C Ripple<br>mV (100kHz) | 125°C Ripple<br>mV (100kHz) |     |
| AVX P/N                        | AVX SRC9000 P/N           | Case |                                     |                               |                               | +25°C<br>(μA) | +85°C<br>(μA) | +125°C<br>(μA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%)                      |                            |                            |                             |                            |                            |                             |     |
| TBJA155*035 J □ # @ 0 ^ ++     | TBJA155*035 J □ LC 9 ^ 45 | A    | 1.5                                 | 35                            | 2000                          | 0.39          | 3.9           | 7.8            | 6            | 9                | 10                                | 0.075                      | 194                        | 174                         | 77                         | 387                        | 349                         | 155 |
| TBJB155*035 R □ # @ 0 ^ ++     | TBJB155*035 R □ LC 9 ^ 45 | B    | 1.5                                 | 35                            | 5460                          | 0.39          | 3.9           | 7.8            | 6            | 9                | 10                                | 0.085                      | 125                        | 112                         | 50                         | 681                        | 613                         | 272 |
| TBJB155*035 J □ # @ 0 ^ ++     | TBJB155*035 J □ LC 9 ^ 45 | B    | 1.5                                 | 35                            | 2500                          | 0.39          | 3.9           | 7.8            | 6            | 9                | 10                                | 0.085                      | 184                        | 166                         | 74                         | 461                        | 415                         | 184 |
| TBJB225*035 R □ # @ 0 ^ ++     | TBJB225*035 R □ LC 9 ^ 45 | B    | 2.2                                 | 35                            | 4550                          | 0.58          | 5.8           | 11.6           | 6            | 9                | 10                                | 0.085                      | 137                        | 123                         | 55                         | 622                        | 560                         | 249 |
| TBJB225*035 J □ # @ 0 ^ ++     | TBJB225*035 J □ LC 9 ^ 45 | B    | 2.2                                 | 35                            | 2000                          | 0.58          | 5.8           | 11.6           | 6            | 9                | 10                                | 0.085                      | 206                        | 186                         | 82                         | 412                        | 371                         | 165 |
| TBJC335*035 R □ # @ 0 ^ ++     | TBJC335*035 R □ LC 9 ^ 45 | B    | 3.3                                 | 35                            | 3740                          | 0.87          | 8.7           | 17.4           | 6            | 9                | 10                                | 0.085                      | 151                        | 136                         | 60                         | 564                        | 507                         | 226 |
| TBJC335*035 J □ # @ 0 ^ ++     | TBJC335*035 J □ LC 9 ^ 45 | B    | 3.3                                 | 35                            | 1000                          | 0.87          | 8.7           | 17.4           | 6            | 9                | 10                                | 0.085                      | 292                        | 262                         | 117                        | 292                        | 262                         | 117 |
| TBJC335*035 R □ # @ 0 ^ ++     | TBJC335*035 R □ LC 9 ^ 45 | C    | 3.3                                 | 35                            | 1840                          | 0.87          | 8.7           | 17.4           | 6            | 9                | 10                                | 0.110                      | 245                        | 220                         | 98                         | 450                        | 405                         | 180 |
| TBJC335*035 J □ # @ 0 ^ ++     | TBJC335*035 J □ LC 9 ^ 45 | C    | 3.3                                 | 35                            | 800                           | 0.87          | 8.7           | 17.4           | 6            | 9                | 10                                | 0.110                      | 371                        | 334                         | 148                        | 297                        | 267                         | 119 |
| TBJD335*035 R □ # @ 0 ^ ++     | TBJD335*035 R □ LC 9 ^ 45 | D    | 3.3                                 | 35                            | 2000                          | 0.87          | 8.7           | 17.4           | 6            | 9                | 10                                | 0.150                      | 274                        | 246                         | 110                        | 548                        | 493                         | 219 |
| TBJB475*035 R □ # @ 0 ^ ++     | TBJB475*035 R □ LC 9 ^ 45 | B    | 4.7                                 | 35                            | 2200                          | 1.2           | 12            | 24             | 6            | 9                | 10                                | 0.085                      | 197                        | 177                         | 79                         | 432                        | 389                         | 173 |
| TBJB475*035 J □ # @ 0 ^ ++     | TBJB475*035 J □ LC 9 ^ 45 | B    | 4.7                                 | 35                            | 1500                          | 1.2           | 12            | 24             | 6            | 9                | 10                                | 0.085                      | 238                        | 214                         | 95                         | 357                        | 321                         | 143 |
| TBJC475*035 R □ # @ 0 ^ ++     | TBJC475*035 R □ LC 9 ^ 45 | C    | 4.7                                 | 35                            | 1410                          | 1.2           | 12            | 24             | 6            | 9                | 10                                | 0.110                      | 279                        | 251                         | 112                        | 394                        | 354                         | 158 |
| TBJC475*035 J □ # @ 0 ^ ++     | TBJC475*035 J □ LC 9 ^ 45 | C    | 4.7                                 | 35                            | 600                           | 1.2           | 12            | 24             | 6            | 9                | 10                                | 0.110                      | 428                        | 385                         | 171                        | 257                        | 231                         | 103 |
| TBJD475*035 R □ # @ 0 ^ ++     | TBJD475*035 R □ LC 9 ^ 45 | D    | 4.7                                 | 35                            | 1500                          | 1.2           | 12            | 24             | 6            | 9                | 10                                | 0.150                      | 316                        | 285                         | 126                        | 474                        | 427                         | 190 |
| TBJC685*035 R □ # @ 0 ^ ++     | TBJC685*035 R □ LC 9 ^ 45 | C    | 6.8                                 | 35                            | 1070                          | 1.8           | 18            | 36             | 6            | 9                | 10                                | 0.110                      | 321                        | 289                         | 128                        | 343                        | 309                         | 137 |
| TBJC685*035 J □ # @ 0 ^ ++     | TBJC685*035 J □ LC 9 ^ 45 | C    | 6.8                                 | 35                            | 600                           | 1.8           | 18            | 36             | 6            | 9                | 10                                | 0.110                      | 428                        | 385                         | 171                        | 257                        | 231                         | 103 |
| TBJD685*035 R □ # @ 0 ^ ++     | TBJD685*035 R □ LC 9 ^ 45 | D    | 6.8                                 | 35                            | 1300                          | 1.8           | 18            | 36             | 6            | 9                | 10                                | 0.150                      | 340                        | 306                         | 136                        | 442                        | 397                         | 177 |
| TBJC106*035 R □ # @ 0 ^ ++     | TBJC106*035 R □ LC 9 ^ 45 | C    | 10                                  | 35                            | 800                           | 2.6           | 26            | 52             | 6            | 9                | 10                                | 0.110                      | 371                        | 334                         | 148                        | 297                        | 267                         | 119 |
| TBJC106*035 J □ # @ 0 ^ ++     | TBJC106*035 J □ LC 9 ^ 45 | C    | 10                                  | 35                            | 600                           | 2.6           | 26            | 52             | 6            | 9                | 10                                | 0.110                      | 428                        | 385                         | 171                        | 257                        | 231                         | 103 |
| TBJD106*035 R □ # @ 0 ^ ++     | TBJD106*035 R □ LC 9 ^ 45 | D    | 10                                  | 35                            | 800                           | 2.6           | 26            | 52             | 6            | 9                | 10                                | 0.150                      | 433                        | 390                         | 173                        | 346                        | 312                         | 139 |
| TBJD106*035 J □ # @ 0 ^ ++     | TBJD106*035 J □ LC 9 ^ 45 | D    | 10                                  | 35                            | 250                           | 2.6           | 26            | 52             | 6            | 9                | 10                                | 0.150                      | 775                        | 697                         | 310                        | 194                        | 174                         | 77  |
| TBJD156*035 R □ # @ 0 ^ ++     | TBJD156*035 R □ LC 9 ^ 45 | D    | 15                                  | 35                            | 720                           | 3.9           | 39            | 78             | 6            | 9                | 10                                | 0.150                      | 456                        | 411                         | 183                        | 329                        | 296                         | 131 |
| TBJD156*035 J □ # @ 0 ^ ++     | TBJD156*035 J □ LC 9 ^ 45 | D    | 15                                  | 35                            | 225                           | 3.9           | 39            | 78             | 6            | 9                | 10                                | 0.150                      | 816                        | 735                         | 327                        | 184                        | 165                         | 73  |
| TBJD226*035 R □ # @ 0 ^ ++     | TBJD226*035 R □ LC 9 ^ 45 | D    | 22                                  | 35                            | 650                           | 5.8           | 58            | 116            | 6            | 9                | 10                                | 0.150                      | 480                        | 432                         | 192                        | 312                        | 281                         | 125 |
| TBJD226*035 J □ # @ 0 ^ ++     | TBJD226*035 J □ LC 9 ^ 45 | D    | 22                                  | 35                            | 200                           | 5.8           | 58            | 116            | 6            | 9                | 10                                | 0.150                      | 866                        | 779                         | 346                        | 173                        | 156                         | 69  |
| TBJE336*035 R □ # @ 0 ^ ++     | TBJE336*035 R □ LC 9 ^ 45 | E    | 33                                  | 35                            | 590                           | 8.7           | 87            | 174            | 6            | 9                | 10                                | 0.165                      | 529                        | 476                         | 212                        | 312                        | 281                         | 125 |
| TBJE336*035 J □ # @ 0 ^ ++     | TBJE336*035 J □ LC 9 ^ 45 | E    | 33                                  | 35                            | 250                           | 8.7           | 87            | 174            | 6            | 9                | 10                                | 0.165                      | 812                        | 731                         | 325                        | 203                        | 183                         | 81  |
| TBJU476*035 R □ # @ 0 ^ ++     | TBJU476*035 R □ LC 9 ^ 45 | U    | 47                                  | 35                            | 400                           | 12.3          | 123           | 246            | 10           | 12               | 12                                | 0.165                      | 642                        | 578                         | 257                        | 257                        | 231                         | 103 |
| TBJU476*035 J □ # @ 0 ^ ++     | TBJU476*035 J □ LC 9 ^ 45 | U    | 47                                  | 35                            | 200                           | 12.3          | 123           | 246            | 10           | 12               | 12                                | 0.165                      | 908                        | 817                         | 363                        | 182                        | 163                         | 73  |
| TBJA224*050 R □ # @ 0 ^ ++     | TBJA224*050 R □ LC 9 ^ 45 | A    | 0.22                                | 50                            | 7500                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 100                        | 90                          | 40                         | 750                        | 675                         | 300 |
| TBJA224*050 J □ # @ 0 ^ ++     | TBJA224*050 J □ LC 9 ^ 45 | A    | 0.22                                | 50                            | 7000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 104                        | 93                          | 41                         | 725                        | 652                         | 290 |
| TBJA334*050 R □ # @ 0 ^ ++     | TBJA334*050 R □ LC 9 ^ 45 | A    | 0.33                                | 50                            | 7000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.075                      | 104                        | 93                          | 41                         | 725                        | 652                         | 290 |
| TBJB474*050 R □ # @ 0 ^ ++     | TBJB474*050 R □ LC 9 ^ 45 | B    | 0.47                                | 50                            | 5000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.085                      | 130                        | 117                         | 52                         | 652                        | 587                         | 261 |
| TBJB684*050 R □ # @ 0 ^ ++     | TBJB684*050 R □ LC 9 ^ 45 | B    | 0.68                                | 50                            | 4000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.085                      | 146                        | 131                         | 58                         | 583                        | 525                         | 233 |
| TBJB684*050 J □ # @ 0 ^ ++     | TBJB684*050 J □ LC 9 ^ 45 | B    | 0.68                                | 50                            | 2000                          | 0.3           | 3             | 6              | 4            | 6                | 8                                 | 0.085                      | 206                        | 186                         | 82                         | 412                        | 371                         | 165 |
| TBJB105*050 R □ # @ 0 ^ ++     | TBJB105*050 R □ LC 9 ^ 45 | B    | 1                                   | 50                            | 3400                          | 0.4           | 4             | 8              | 4            | 6                | 8                                 | 0.085                      | 158                        | 142                         | 63                         | 538                        | 484                         | 215 |
| TBJB105*050 J □ # @ 0 ^ ++     | TBJB105*050 J □ LC 9 ^ 45 | B    | 1                                   | 50                            | 2000                          | 0.4           | 4             | 8              | 4            | 6                | 8                                 | 0.085                      | 206                        | 186                         | 82                         | 412                        | 371                         | 165 |
| TBJC105*050 R □ # @ 0 ^ ++     | TBJC105*050 R □ LC 9 ^ 45 | C    | 1                                   | 50                            | 3000                          | 0.4           | 4             | 8              | 4            | 6                | 8                                 | 0.110                      | 191                        | 172                         | 77                         | 574                        | 517                         | 230 |
| TBJC155*050 R □ # @ 0 ^ ++     | TBJC155*050 R □ LC 9 ^ 45 | C    | 1.5                                 | 50                            | 2500                          | 0.6           | 6             | 12             | 6            | 9                | 10                                | 0.110                      | 210                        | 189                         | 84                         | 524                        | 472                         | 210 |
| TBJC155*050 J □ # @ 0 ^ ++     | TBJC155*050 J □ LC 9 ^ 45 | C    | 1.5                                 | 50                            | 1500                          | 0.6           | 6             | 12             | 6            | 9                | 10                                | 0.110                      | 271                        | 244                         | 108                        | 406                        | 366                         | 162 |
| TBJC225*050 R □ # @ 0 ^ ++     | TBJC225*050 R □ LC 9 ^ 45 | C    | 2.2                                 | 50                            | 1700                          | 0.8           | 8             | 16             | 6            | 9                | 10                                | 0.110                      | 254                        | 229                         | 102                        | 432                        | 389                         | 173 |
| TBJC225*050 J □ # @ 0 ^ ++     | TBJC225*050 J □ LC 9 ^ 45 | C    | 2.2                                 | 50                            | 1000                          | 0.8           | 8             | 16             | 6            | 9                | 10                                | 0.110                      | 332                        | 298                         | 133                        | 332                        | 298                         | 133 |
| TBJD225*050 R □ # @ 0 ^ ++     | TBJD225*050 R □ LC 9 ^ 45 | D    | 2.2                                 | 50                            | 2000                          | 0.8           | 8             | 16             | 4.5          | 7                | 9                                 | 0.150                      | 274                        | 246                         | 110                        | 548                        | 493                         | 219 |
| TBJD225*050 J □ # @ 0 ^ ++     | TBJD225*050 J □ LC 9 ^ 45 | D    | 2.2                                 | 50                            | 1200                          | 0.8           | 8             | 16             | 4.5          | 7                | 9                                 | 0.150                      | 354                        | 318                         | 141                        | 424                        | 382                         | 170 |
| TBJC335*050 R □ # @ 0 ^ ++     | TBJC335*050 R □ LC 9 ^ 45 | C    | 3.3                                 | 50                            | 1400                          | 1.2           | 12            | 24             | 6            | 9                | 10                                | 0.110                      | 280                        | 252                         | 112                        | 392                        | 353                         | 157 |
| TBJC335*050 J □ # @ 0 ^ ++     | TBJC335*050 J □ LC 9 ^ 45 | C    | 3.3                                 | 50                            | 1000                          | 1.2           | 12            | 24             | 6            | 9                | 10                                | 0.110                      | 332                        | 298                         | 133                        | 332                        | 298                         | 133 |
| TBJD335*050 R □ # @ 0 ^ ++     | TBJD335*050 R □ LC 9 ^ 45 | D    | 3.3                                 | 50                            | 1100                          | 1.2           | 12            | 24             | 4.5          | 7                | 9                                 | 0.150                      | 369                        | 332                         | 148                        | 406                        | 366                         | 162 |
| TBJD335*050 J □ # @ 0 ^ ++     | TBJD335*050 J □ LC 9 ^ 45 | D    | 3.3                                 | 50                            | 800                           | 1.2           | 12            | 24             | 4.5          | 7                | 9                                 | 0.150                      | 433                        | 390                         | 173                        | 346                        | 312                         | 139 |
| TBJD475*050 R □ # @ 0 ^ ++     | TBJD475*050 R □ LC 9 ^ 45 | D    | 4.7                                 | 50                            | 900                           | 1.8           | 18            | 36             | 4.5          | 7                | 9                                 | 0.150                      | 408                        | 367                         | 163                        | 367                        | 331                         | 147 |
| TBJD475*050 J □ # @ 0 ^ ++     | TBJD475*050 J □ LC 9 ^ 45 | D    | 4.7                                 | 50                            | 600                           | 1.8           | 18            | 36             | 4.5          | 7                | 9                                 | 0.150                      | 500                        | 450                         | 200                        | 300                        | 270                         | 120 |
| TBJD685*050 R □ # @ 0 ^ ++     | TBJD685*050 R □ LC 9 ^ 45 | D    | 6.8                                 | 50                            | 700                           | 2.6           | 26            | 52             | 4.5          | 7                | 9                                 | 0.150                      | 463                        | 417                         | 185                        | 324                        | 292                         | 130 |
| TBJE106*050 R □ # @ 0 ^ ++     | TBJE106*050 R □ LC 9 ^ 45 | E    | 10                                  | 50                            | 700                           | 3.8           | 38            | 76             | 4.5          | 7                | 9                                 | 0.165                      | 486                        | 437                         | 194                        | 340                        | 306                         | 136 |
| TBJE106*050 J □ # @ 0 ^ ++     | TBJE106*050 J □ LC 9 ^ 45 | E    | 10                                  | 50                            | 300                           | 3.8           | 38            | 76             | 4.5          | 7                | 9                                 | 0.165                      | 742                        | 667                         | 297                        | 222                        | 200                         | 89  |
| TBJU156*050 R □ # @ 0 ^ ++     | TBJU156*050 R □ LC 9 ^ 45 | U    | 15                                  | 50                            | 500                           | 5.6           | 56            | 112            | 30           | 45               | 45                                | 0.165                      | 574                        | 517                         | 230                        | 287                        | 259                         | 115 |
| TBJU226*050 R □ # @ 0 ^ ++     | TBJU226*050 R □ LC 9 ^ 45 | U    | 22                                  | 50                            | 500                           | 8.2           | 82            | 164            | 30           | 45               | 45                                | 0.165                      | 574                        | 517                         | 230                        | 287                        | 259                         | 115 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.



**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**



# DSCC Dwgs 07016 & 95158



## COTS-Plus



### MARKING

(Brown marking on gold body)



**Polarity Stripe (+)**  
**Capacitance Code**  
**Rated Voltage**  
**Manufacturer's ID**  
**Lot Number**

The DSCC 07016 & 95158 families, based on the CWR11 form factor, are high reliability series encompassing the current range of EIA Low ESR ratings. DSCC 07016 has the widest range of case sizes, capacitance / voltage ratings, and is offered with Weibull Grade "B" and "C" reliability with all MIL-PRF-55365 Rev. G surge test options ("A", "B" & "C").

For Space Level applications, AVX SRC9000 qualification is recommend. Please refer to the TBJ COTS-Plus SRC9000 datasheet for part number availability.

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these correspond to "H", "K", "C" and "B" termination, respectively, per MIL-PRF-55365).

The molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.

### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|------------|----------------|------------------------------|------------------------------|------------------------------|------------------------------|--------------|
| A    | 1206     | 3216-18    | 3.20 (0.126)   | 1.60 (0.063)                 | 1.60 (0.063)                 | 1.20 (0.047)                 | 0.80 (0.031)                 | 1.10 (0.043) |
| B    | 1210     | 3528-21    | 3.50 (0.138)   | 2.80 (0.110)                 | 1.90 (0.075)                 | 2.20 (0.087)                 | 0.80 (0.031)                 | 1.40 (0.055) |
| C    | 2312     | 6032-28    | 6.00 (0.236)   | 3.20 (0.126)                 | 2.60 (0.102)                 | 2.20 (0.087)                 | 1.30 (0.051)                 | 2.90 (0.114) |
| D    | 2917     | 7343-31    | 7.30 (0.287)   | 4.30 (0.169)                 | 2.90 (0.114)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| E    | 2917     | 7343-43    | 7.30 (0.287)   | 4.30 (0.169)                 | 4.10 (0.162)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| V    | 2924     | 7361-38    | 7.30 (0.287)   | 6.10 (0.240)                 | 3.55 (0.140)                 | 3.10 (0.120)                 | 1.30 (0.051)                 | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (EIA VOLTAGE CODE) RANGE LETTER DENOTES CASE SIZE (ESR LIMITS IN PARENTHESES)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) to 85°C |                         |                               |                          |                         |                                 |                              |                 |
|-------------|------|--|-------------------------|-------------------------------|--------------------------|-------------------------|---------------------------------|------------------------------|-----------------|
| µF          | Code | 4V (G)                                     | 6V (J)                  | 10V (A)                       | 16V (C)                  | 20V (D)                 | 25V (E)                         | 35V (V)                      | 50V (T)         |
| 0.15        | 154  |  |                         |                               |                          |                         |                                 |                              | A(15000)        |
| 0.22        | 224  |  |                         |                               |                          |                         |                                 |                              | A(18000)        |
| 0.47        | 474  |  |                         |                               |                          |                         |                                 | A(12000)                     | A(9500)/B(9500) |
| 0.68        | 684  |  |                         |                               |                          |                         | A(10000)                        | A(8000)                      | A(7900)         |
| 1.0         | 105  |  |                         |                               |                          |                         | A(8000)                         | A(7500)                      | A(6600)/B(7000) |
| 1.5         | 155  |  |                         |                               |                          | A(6500)                 | A(3000,7500)                    | A(7500)/B(5200)              | C(2000)/D(1500) |
| 2.2         | 225  |  |                         |                               | A(5500)                  | A(3000)                 | A(7000)/B(2000)                 | B(2000)                      | D(1200)         |
| 3.3         | 335  |  | A(8000)                 |                               | A(3500,5000)             |                         | B(2000)                         | B(1000)                      | D(800)          |
| 4.7         | 475  |  | A(6000)                 | A(5000)                       | A(2000)                  | A(1800,4000)<br>B(1000) | A(3100)<br>B(700,1500)          | B(1500)<br>C(600)/D(450)     | D(300)          |
| 6.8         | 685  |  | A(5000)                 | A(4000)                       | A(1500)/B(1200)          | B(1000)                 | B(700,2800)<br>C(700)           | C(350)/D(400)<br>E(300)      | D(300,600)      |
| 10          | 106  |  | A(4000)                 | A(1800,3000)                  | A(3000)/B(900)           | B(500,1000)<br>C(700)   | C(300,500)                      | C(1600)/D(125,300)<br>E(250) |                 |
| 15          | 156  |  | A(3500)                 | A(1000,3200)<br>B(600)        | B(500,800)               | B(500)/C(450)<br>D(275) | D(275)/E(200)                   | C(450)/D(100,300)<br>E(225)  |                 |
| 22          | 226  |  | A(3000)/B(600)          | B(500,700)<br>C(300)          | B(500,600)<br>C(150,375) | B(600)/C(400)<br>D(275) | C(275,400)<br>D(100,200)/E(225) | D(125,400)<br>E(125,300)     |                 |
| 33          | 336  | A(3000)                                    | B(600)                  | A(700)/B(425,650)<br>C(500)   | C(100,300)<br>D(250)     | C(300)<br>D(100,200)    | D(90,300)<br>E(100,175)         | D(200,300)<br>E(300)         |                 |
| 47          | 476  |  | C(300)                  | C(200,350)<br>D(200)          | C(110,350)<br>D(80,200)  | D(100,200)<br>E(150)    | D(175,250)                      | E(250)/V(200)                |                 |
| 68          | 686  | A(1500)                                    | B(500)/C(200)<br>D(175) | C(80,300)<br>D(150)/E(150)    | D(150)                   | D(70,200)<br>E(150,200) | V(95)                           |                              |                 |
| 100         | 107  | A(1400)<br>B(900)                          | C(75,150)               | C(75,200)<br>D(50,100)/E(100) | D(50,125)<br>E(125)      | V(60)                   |                                 |                              |                 |
| 150         | 157  |  | D(125)/E(125)           | D(50,100)/E(100)              | D(60,150)/V(45)          |                         |                                 |                              |                 |
| 220         | 227  |  | D(100,125)<br>E(100)    | D(50,150)<br>E(50,100)        | V(50)                    |                         |                                 |                              |                 |
| 330         | 337  |  | E(50,150)               | D(50,150)<br>E(50,100)/V(40)  |                          |                         |                                 |                              |                 |
| 470         | 477  |  | E(50,200)/V(40)         | E(50,200)/V(40)               |                          |                         |                                 |                              |                 |
| 1000        | 108  | E(200)                                     |                         |                               |                          |                         |                                 |                              |                 |

NOTE: EIA standards for Low ESR solid tantalum capacitors allow an ESR movement of 1.25 times initial limit post mounting.

# DSCC Dwgs 07016 & 95158




## COTS-Plus

### HOW TO ORDER


#### DSCC DWG P/N:

|   |   |  |  |   |  |
|---|---|--|--|---|--|
| <p><b>07016</b></p> <hr style="width: 50%; margin: auto;"/> <p>DSCC DWG<br/>07016</p> | <p><b>-001</b></p> <hr style="width: 50%; margin: auto;"/> <p>Dash<br/>Number<br/>See Rating<br/>Tables</p> | <p><b>K</b></p> <hr style="width: 50%; margin: auto;"/> <p>Capacitance<br/>Tolerance<br/>K = ±10%<br/>M = ±20%</p> | <p><b>B</b></p> <hr style="width: 50%; margin: auto;"/> <p>Reliability<br/>Grade<br/>B = B Weibull<br/>C = C Weibull<br/>D = D Weibull</p> | <p><b>C</b></p> <hr style="width: 50%; margin: auto;"/> <p>Termination Finish<br/>B = Gold Plated (10 microinch minimum)<br/>H = Solder Plated (50 microinch minimum)<br/>C = Hot Solder Dip (60 microinch minimum)</p> | <p><b>A</b></p> <hr style="width: 50%; margin: auto;"/> <p>Surge Test<br/>Option<br/>A = 10 cycles, +25°C<br/>B = 10 cycles,<br/>-55°C &amp; +85°C<br/>C = 10 cycles,<br/>-55°C &amp; +85°C<br/>before Weibull<br/>Z = None required<br/>Per MIL-PRF-55365</p> |
|---|---|--|--|---|--|



For RoHS compliant products,  
please select correct termination style.

|   |  |  |  |
|---|--|--|--|
| <p><b>95158</b></p> <hr style="width: 50%; margin: auto;"/> <p>DSCC DWG<br/>95158</p> | <p><b>-01</b></p> <hr style="width: 50%; margin: auto;"/> <p>Dash<br/>Number<br/>See Rating<br/>Tables</p> | <p><b>K</b></p> <hr style="width: 50%; margin: auto;"/> <p>Capacitance<br/>Tolerance<br/>K = ±10%<br/>M = ±20%</p> | <p><b>H</b></p> <hr style="width: 50%; margin: auto;"/> <p>Termination Finish<br/>B = Gold Plated (10 microinch minimum)<br/>H = Solder Plated (100 microinch minimum)</p> |
|---|--|--|--|



For RoHS compliant products,  
please select correct termination style.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |   |    |    |    |    |    |    |  |
|------------------------------------|---|-----|---|----|----|----|----|----|----|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |   |    |    |    |    |    |    |  |
| Capacitance Range:                 | 0.15 µF to 1000 µF  |     |   |    |    |    |    |    |    |  |
| Capacitance Tolerance:             | ±10%; ±20%  |     |   |    |    |    |    |    |    |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6 | 10 | 16 | 20 | 25 | 35 | 50 |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4 | 7  | 10 | 13 | 17 | 23 | 33 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 5.2 | 8 | 13 | 20 | 26 | 32 | 46 | 65 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 3.4 | 5 | 8  | 12 | 16 | 20 | 28 | 40 |  |
| Temperature Range:                 | -55°C to +125°C   |     |   |    |    |    |    |    |    |  |

# DSCC Dwgs 07016 & 95158



## COTS-Plus

| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating per DSCC 95158 or 07016 where applicable |                               |                               |               |               |                |              |                    |              | Typical RMS Ripple Data by Rating |                           |                           |                            |                           |                           |                            |
|--------------------------------|------|--|-------------------------------|-------------------------------|---------------|---------------|----------------|--------------|--------------------|--------------|-----------------------------------|---------------------------|---------------------------|----------------------------|---------------------------|---------------------------|----------------------------|
|                                |      | Cap @ 120Hz<br>µF @ 25°C   | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>mOhms @ +25°C | DCL max       |               |                | DF Max       |                    |              | Power Dissipation<br>W            | 25°C Ripple<br>A (100kHz) | 85°C Ripple<br>A (100kHz) | 125°C Ripple<br>A (100kHz) | 25°C Ripple<br>V (100kHz) | 85°C Ripple<br>V (100kHz) | 125°C Ripple<br>V (100kHz) |
|                                |      |  |                               |                               | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +(85/125)°C<br>(%) | -55°C<br>(%) |                                   |                           |                           |                            |                           |                           |                            |
| DSCC P/N                       | Case |  |                               |                               |               |               |                |              |                    |              |                                   |                           |                           |                            |                           |                           |                            |
| 07016 001 * @ ^+ A             | A    | 33   | 4                             | 3000                          | 1.4           | 14            | 17             | 6            | 9                  | 9            | 0.075                             | 0.16                      | 0.14                      | 0.06                       | 0.47                      | 0.43                      | 0.19                       |
| 07016 002 * @ ^+ A             | A    | 68   | 4                             | 1500                          | 2.7           | 27            | 32             | 10           | 12                 | 14           | 0.075                             | 0.22                      | 0.20                      | 0.09                       | 0.34                      | 0.30                      | 0.13                       |
| 07016 003 * @ ^+ A             | A    | 100  | 4                             | 1400                          | 4             | 40            | 48             | 30           | 36                 | 42           | 0.075                             | 0.23                      | 0.21                      | 0.09                       | 0.32                      | 0.29                      | 0.13                       |
| 07016 004 * @ ^+ B             | B    | 100  | 4                             | 900                           | 4             | 40            | 48             | 8            | 10                 | 12           | 0.085                             | 0.31                      | 0.28                      | 0.12                       | 0.28                      | 0.25                      | 0.11                       |
| 07016 005 * @ ^+ E             | E    | 1,000  | 4                             | 200                           | 40            | 400           | 480            | 60           | 90                 | 90           | 0.165                             | 0.91                      | 0.82                      | 0.36                       | 0.18                      | 0.16                      | 0.07                       |
| 07016 006 * @ ^+ A             | A    | 3.3  | 6                             | 8000                          | 0.5           | 5             | 6              | 6            | 9                  | 9            | 0.075                             | 0.10                      | 0.09                      | 0.04                       | 0.77                      | 0.70                      | 0.31                       |
| 07016 007 * @ ^+ A             | A    | 4.7  | 6                             | 6000                          | 0.5           | 5             | 6              | 6            | 9                  | 10           | 0.075                             | 0.11                      | 0.10                      | 0.04                       | 0.67                      | 0.60                      | 0.27                       |
| 07016 008 * @ ^+ A             | A    | 6.8  | 6                             | 5000                          | 0.5           | 5             | 6              | 6            | 9                  | 10           | 0.075                             | 0.12                      | 0.11                      | 0.05                       | 0.61                      | 0.55                      | 0.24                       |
| 07016 009 * @ ^+ A             | A    | 10   | 6                             | 4000                          | 0.6           | 10            | 11             | 6            | 9                  | 10           | 0.075                             | 0.14                      | 0.12                      | 0.05                       | 0.55                      | 0.49                      | 0.22                       |
| 07016 010 * @ ^+ A             | A    | 15   | 6                             | 3500                          | 0.9           | 10            | 11             | 6            | 9                  | 10           | 0.075                             | 0.15                      | 0.13                      | 0.06                       | 0.51                      | 0.46                      | 0.20                       |
| 07016 011 * @ ^+ A             | A    | 22   | 6                             | 3000                          | 1.4           | 14            | 17             | 6            | 9                  | 10           | 0.075                             | 0.16                      | 0.14                      | 0.06                       | 0.47                      | 0.43                      | 0.19                       |
| 07016 012 * @ ^+ B             | B    | 22   | 6                             | 600                           | 1.4           | 14            | 17             | 6            | 9                  | 10           | 0.085                             | 0.38                      | 0.34                      | 0.15                       | 0.23                      | 0.20                      | 0.09                       |
| 07016 013 * @ ^+ B             | B    | 33   | 6                             | 600                           | 2.1           | 21            | 25             | 6            | 9                  | 10           | 0.085                             | 0.38                      | 0.34                      | 0.15                       | 0.23                      | 0.20                      | 0.09                       |
| 07016 014 * @ ^+ C             | C    | 47   | 6                             | 300                           | 3             | 30            | 36             | 6            | 9                  | 10           | 0.110                             | 0.61                      | 0.54                      | 0.24                       | 0.18                      | 0.16                      | 0.07                       |
| 07016 015 * @ ^+ B             | B    | 68   | 6                             | 500                           | 4.3           | 43            | 51             | 8            | 10                 | 12           | 0.085                             | 0.41                      | 0.37                      | 0.16                       | 0.21                      | 0.19                      | 0.08                       |
| 07016 016 * @ ^+ C             | C    | 68   | 6                             | 200                           | 4.3           | 43            | 51             | 6            | 9                  | 10           | 0.110                             | 0.74                      | 0.67                      | 0.30                       | 0.15                      | 0.13                      | 0.06                       |
| 95158 01 * ^ D                 | D    | 68   | 6                             | 175                           | 3.3           | 19.8          | 33             | 4            | 6                  | 6            | 0.150                             | 0.93                      | 0.83                      | 0.37                       | 0.16                      | 0.15                      | 0.06                       |
| 07016 017 * @ ^+ C             | C    | 100  | 6                             | 150                           | 6.3           | 63            | 76             | 6            | 9                  | 10           | 0.110                             | 0.86                      | 0.77                      | 0.34                       | 0.13                      | 0.12                      | 0.05                       |
| 07016 018 * @ ^+ C             | C    | 100  | 6                             | 75                            | 6.3           | 63            | 76             | 6            | 9                  | 10           | 0.110                             | 1.21                      | 1.09                      | 0.48                       | 0.09                      | 0.08                      | 0.04                       |
| 07016 019 * @ ^+ D             | D    | 150  | 6                             | 125                           | 9.5           | 95            | 113            | 6            | 9                  | 10           | 0.150                             | 1.10                      | 0.99                      | 0.44                       | 0.14                      | 0.12                      | 0.05                       |
| 95158 02 * ^ E                 | E    | 150  | 6                             | 125                           | 7.2           | 43.2          | 72             | 6            | 8                  | 8            | 0.165                             | 1.15                      | 1.03                      | 0.46                       | 0.14                      | 0.13                      | 0.06                       |
| 07016 020 * @ ^+ D             | D    | 220  | 6                             | 125                           | 13.9          | 139           | 166            | 8            | 10                 | 12           | 0.150                             | 1.10                      | 0.99                      | 0.44                       | 0.14                      | 0.12                      | 0.05                       |
| 95158 25 * ^ D                 | D    | 220  | 6                             | 100                           | 13.2          | 132           | 165            | 8            | 10                 | 12           | 0.150                             | 1.22                      | 1.10                      | 0.49                       | 0.12                      | 0.11                      | 0.05                       |
| 95158 03 * ^ E                 | E    | 220  | 6                             | 100                           | 13.2          | 132           | 165            | 8            | 12                 | 12           | 0.165                             | 1.28                      | 1.16                      | 0.51                       | 0.13                      | 0.12                      | 0.05                       |
| 07016 021 * @ ^+ E             | E    | 330  | 6                             | 150                           | 20.8          | 208           | 249            | 8            | 10                 | 12           | 0.165                             | 1.05                      | 0.94                      | 0.42                       | 0.16                      | 0.14                      | 0.06                       |
| 07016 022 * @ ^+ E             | E    | 330  | 6                             | 50                            | 20.8          | 208           | 249            | 8            | 10                 | 12           | 0.165                             | 1.82                      | 1.63                      | 0.73                       | 0.09                      | 0.08                      | 0.04                       |
| 07016 023 M @ ^+ E             | E    | 470  | 6                             | 200                           | 29.6          | 296           | 355            | 10           | 12                 | 14           | 0.165                             | 0.91                      | 0.82                      | 0.36                       | 0.18                      | 0.16                      | 0.07                       |
| 07016 024 M @ ^+ E             | E    | 470  | 6                             | 50                            | 29.6          | 296           | 355            | 10           | 12                 | 14           | 0.165                             | 1.82                      | 1.63                      | 0.73                       | 0.09                      | 0.08                      | 0.04                       |
| 07016 025 * @ ^+ V             | V    | 470  | 6                             | 40                            | 29.6          | 296           | 355            | 10           | 12                 | 12           | 0.250                             | 2.50                      | 2.25                      | 1.00                       | 0.10                      | 0.09                      | 0.04                       |
| 07016 026 * @ ^+ A             | A    | 4.7  | 10                            | 5000                          | 0.5           | 5             | 6              | 6            | 9                  | 10           | 0.075                             | 0.12                      | 0.11                      | 0.05                       | 0.61                      | 0.55                      | 0.24                       |
| 07016 027 * @ ^+ A             | A    | 6.8  | 10                            | 4000                          | 0.7           | 7             | 8              | 6            | 9                  | 10           | 0.075                             | 0.14                      | 0.12                      | 0.05                       | 0.55                      | 0.49                      | 0.22                       |
| 07016 028 * @ ^+ A             | A    | 10   | 10                            | 3000                          | 1             | 10            | 12             | 6            | 9                  | 10           | 0.075                             | 0.16                      | 0.14                      | 0.06                       | 0.47                      | 0.43                      | 0.19                       |
| 07016 029 * @ ^+ A             | A    | 10   | 10                            | 1800                          | 1             | 10            | 12             | 6            | 9                  | 10           | 0.075                             | 0.20                      | 0.18                      | 0.08                       | 0.37                      | 0.33                      | 0.15                       |
| 07016 030 * @ ^+ A             | A    | 15   | 10                            | 3200                          | 1.6           | 16            | 19             | 6            | 9                  | 10           | 0.075                             | 0.15                      | 0.14                      | 0.06                       | 0.49                      | 0.44                      | 0.20                       |
| 07016 031 * @ ^+ A             | A    | 15   | 10                            | 1000                          | 1.6           | 16            | 19             | 6            | 9                  | 10           | 0.075                             | 0.27                      | 0.25                      | 0.11                       | 0.27                      | 0.25                      | 0.11                       |
| 07016 032 * @ ^+ B             | B    | 15   | 10                            | 600                           | 1.6           | 16            | 19             | 6            | 9                  | 10           | 0.085                             | 0.38                      | 0.34                      | 0.15                       | 0.23                      | 0.20                      | 0.09                       |
| 07016 033 * @ ^+ B             | B    | 22   | 10                            | 700                           | 2.2           | 22            | 26             | 6            | 9                  | 10           | 0.085                             | 0.35                      | 0.31                      | 0.14                       | 0.24                      | 0.22                      | 0.10                       |
| 07016 034 * @ ^+ B             | B    | 22   | 10                            | 500                           | 2.2           | 22            | 26             | 6            | 9                  | 10           | 0.085                             | 0.41                      | 0.37                      | 0.16                       | 0.21                      | 0.19                      | 0.08                       |
| 07016 035 * @ ^+ C             | C    | 22   | 10                            | 300                           | 2.2           | 22            | 26             | 6            | 9                  | 10           | 0.110                             | 0.61                      | 0.54                      | 0.24                       | 0.18                      | 0.16                      | 0.07                       |
| 07016 036 * @ ^+ A             | A    | 33   | 10                            | 700                           | 3.3           | 33            | 40             | 8            | 10                 | 12           | 0.075                             | 0.33                      | 0.29                      | 0.13                       | 0.23                      | 0.21                      | 0.09                       |
| 07016 037 * @ ^+ B             | B    | 33   | 10                            | 650                           | 3.3           | 33            | 40             | 6            | 9                  | 10           | 0.085                             | 0.36                      | 0.33                      | 0.14                       | 0.24                      | 0.21                      | 0.09                       |
| 07016 038 * @ ^+ B             | B    | 33   | 10                            | 425                           | 3.3           | 33            | 40             | 6            | 9                  | 10           | 0.085                             | 0.45                      | 0.40                      | 0.18                       | 0.19                      | 0.17                      | 0.08                       |
| 07016 039 * @ ^+ C             | C    | 33   | 10                            | 500                           | 3.3           | 33            | 40             | 6            | 9                  | 10           | 0.110                             | 0.47                      | 0.42                      | 0.19                       | 0.23                      | 0.21                      | 0.09                       |
| 07016 040 * @ ^+ C             | C    | 47   | 10                            | 350                           | 4.7           | 47            | 56             | 6            | 9                  | 10           | 0.110                             | 0.56                      | 0.50                      | 0.22                       | 0.20                      | 0.18                      | 0.08                       |
| 07016 041 * @ ^+ C             | C    | 47   | 10                            | 200                           | 4.7           | 47            | 56             | 6            | 9                  | 10           | 0.110                             | 0.74                      | 0.67                      | 0.30                       | 0.15                      | 0.13                      | 0.06                       |
| 95158 -04 * ^ D                | D    | 47   | 10                            | 200                           | 3.8           | 22.8          | 38             | 4            | 6                  | 6            | 0.150                             | 0.87                      | 0.78                      | 0.35                       | 0.17                      | 0.16                      | 0.07                       |
| 07016 042 * @ ^+ C             | C    | 68   | 10                            | 300                           | 6.8           | 68            | 82             | 8            | 10                 | 12           | 0.110                             | 0.61                      | 0.54                      | 0.24                       | 0.18                      | 0.16                      | 0.07                       |
| 07016 043 * @ ^+ C             | C    | 68   | 10                            | 80                            | 6.8           | 68            | 82             | 8            | 10                 | 12           | 0.110                             | 1.17                      | 1.06                      | 0.47                       | 0.09                      | 0.08                      | 0.04                       |
| 07016 044 * @ ^+ D             | D    | 68   | 10                            | 150                           | 6.8           | 68            | 82             | 6            | 9                  | 10           | 0.150                             | 1.00                      | 0.90                      | 0.40                       | 0.15                      | 0.14                      | 0.06                       |
| 95158 05 * ^ E                 | E    | 68   | 10                            | 150                           | 5.4           | 32.4          | 54             | 4            | 6                  | 6            | 0.165                             | 1.05                      | 0.94                      | 0.42                       | 0.16                      | 0.14                      | 0.06                       |
| 07016 045 * @ ^+ C             | C    | 100  | 10                            | 200                           | 10            | 100           | 120            | 8            | 10                 | 12           | 0.110                             | 0.74                      | 0.67                      | 0.30                       | 0.15                      | 0.13                      | 0.06                       |
| 07016 046 * @ ^+ C             | C    | 100  | 10                            | 75                            | 10            | 100           | 120            | 8            | 10                 | 12           | 0.110                             | 1.21                      | 1.09                      | 0.48                       | 0.09                      | 0.08                      | 0.04                       |
| 95158 06 * ^ D                 | D    | 100  | 10                            | 100                           | 10            | 100           | 125            | 8            | 12                 | 12           | 0.150                             | 1.22                      | 1.10                      | 0.49                       | 0.12                      | 0.11                      | 0.05                       |
| 07016 047 * @ ^+ D             | D    | 100  | 10                            | 50                            | 10            | 100           | 120            | 6            | 9                  | 10           | 0.150                             | 1.73                      | 1.56                      | 0.69                       | 0.09                      | 0.08                      | 0.03                       |
| 95158 07 * ^ E                 | E    | 100  | 10                            | 100                           | 8             | 48            | 80             | 6            | 8                  | 8            | 0.165                             | 1.28                      | 1.16                      | 0.51                       | 0.13                      | 0.12                      | 0.05                       |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# DSCC Dwgs 07016 & 95158



## COTS-Plus

| RATING & PART NUMBER REFERENCE |         | Parametric Specifications by Rating per DSCC 95158 or 07016 where applicable |                               |                               |               |               |                |              |                    |              | Typical RMS Ripple Data by Rating |                           |                           |                            |                           |                           |                            |
|--------------------------------|---------|--|-------------------------------|-------------------------------|---------------|---------------|----------------|--------------|--------------------|--------------|-----------------------------------|---------------------------|---------------------------|----------------------------|---------------------------|---------------------------|----------------------------|
|                                |         | Cap @ 120Hz<br>µF @ 25°C   | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>mOhms @ +25°C | DCL max       |               |                | DF Max       |                    |              | Power Dissipation<br>W            | 25°C Ripple<br>A (100kHz) | 85°C Ripple<br>A (100kHz) | 125°C Ripple<br>A (100kHz) | 25°C Ripple<br>V (100kHz) | 85°C Ripple<br>V (100kHz) | 125°C Ripple<br>V (100kHz) |
|                                |         |  |                               |                               | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +(85/125)°C<br>(%) | -55°C<br>(%) |                                   |                           |                           |                            |                           |                           |                            |
| DSCC P/N                       | Case    |  |                               |                               |               |               |                |              |                    |              |                                   |                           |                           |                            |                           |                           |                            |
| 95158 26                       | * ^ A   | D  | 150                           | 10                            | 100           | 15            | 150            | 187.5        | 8                  | 10           | 12                                | 0.150                     | 1.22                      | 1.10                       | 0.49                      | 0.11                      | 0.05                       |
| 07016 048                      | * @ ^ + | D  | 150                           | 10                            | 50            | 15            | 150            | 180          | 8                  | 10           | 12                                | 0.150                     | 1.73                      | 1.56                       | 0.69                      | 0.09                      | 0.08                       |
| 95158 08                       | * ^ A   | E  | 150                           | 10                            | 100           | 15            | 150            | 187.5        | 8                  | 12           | 12                                | 0.165                     | 1.28                      | 1.16                       | 0.51                      | 0.13                      | 0.12                       |
| 07016 049                      | * @ ^ + | D  | 220                           | 10                            | 150           | 22            | 220            | 264          | 8                  | 10           | 12                                | 0.150                     | 1.00                      | 0.90                       | 0.40                      | 0.15                      | 0.14                       |
| 07016 050                      | M @ ^ + | D  | 220                           | 10                            | 50            | 15            | 150            | 180          | 8                  | 10           | 12                                | 0.150                     | 1.73                      | 1.56                       | 0.69                      | 0.09                      | 0.08                       |
| 95158 28                       | * ^ A   | E  | 220                           | 10                            | 100           | 15            | 150            | 187.5        | 8                  | 10           | 12                                | 0.165                     | 1.28                      | 1.16                       | 0.51                      | 0.13                      | 0.12                       |
| 07016 051                      | * @ ^ + | E  | 220                           | 10                            | 50            | 22            | 220            | 264          | 8                  | 10           | 12                                | 0.165                     | 1.82                      | 1.63                       | 0.73                      | 0.09                      | 0.08                       |
| 07016 052                      | M @ ^ + | D  | 330                           | 10                            | 150           | 33            | 330            | 396          | 8                  | 10           | 12                                | 0.150                     | 1.00                      | 0.90                       | 0.40                      | 0.15                      | 0.14                       |
| 07016 053                      | M @ ^ + | D  | 330                           | 10                            | 50            | 33            | 330            | 396          | 8                  | 10           | 12                                | 0.150                     | 1.73                      | 1.56                       | 0.69                      | 0.09                      | 0.08                       |
| 07016 054                      | * @ ^ + | E  | 330                           | 10                            | 100           | 33            | 330            | 396          | 8                  | 10           | 12                                | 0.165                     | 1.28                      | 1.16                       | 0.51                      | 0.13                      | 0.12                       |
| 07016 055                      | * @ ^ + | E  | 330                           | 10                            | 50            | 33            | 330            | 396          | 8                  | 10           | 12                                | 0.165                     | 1.82                      | 1.63                       | 0.73                      | 0.09                      | 0.08                       |
| 07016 056                      | * @ ^ + | V  | 330                           | 10                            | 40            | 33            | 330            | 396          | 8                  | 10           | 12                                | 0.250                     | 2.50                      | 2.25                       | 1.00                      | 0.10                      | 0.09                       |
| 07016 057                      | M @ ^ + | E  | 470                           | 10                            | 200           | 47            | 470            | 564          | 10                 | 12           | 14                                | 0.165                     | 0.91                      | 0.82                       | 0.36                      | 0.18                      | 0.16                       |
| 07016 058                      | M @ ^ + | E  | 470                           | 10                            | 50            | 47            | 470            | 564          | 10                 | 12           | 14                                | 0.165                     | 1.82                      | 1.63                       | 0.73                      | 0.09                      | 0.08                       |
| 07016 059                      | * @ ^ + | V  | 470                           | 10                            | 40            | 47            | 470            | 564          | 10                 | 12           | 14                                | 0.250                     | 2.50                      | 2.25                       | 1.00                      | 0.09                      | 0.04                       |
| 07016 060                      | * @ ^ + | A  | 2.2                           | 16                            | 5500          | 0.5           | 5              | 6            | 6                  | 9            | 10                                | 0.075                     | 0.12                      | 0.11                       | 0.05                      | 0.64                      | 0.58                       |
| 07016 061                      | * @ ^ + | A  | 3.3                           | 16                            | 5000          | 0.5           | 5              | 6            | 6                  | 9            | 10                                | 0.075                     | 0.12                      | 0.11                       | 0.05                      | 0.61                      | 0.55                       |
| 07016 062                      | * @ ^ + | A  | 3.3                           | 16                            | 3500          | 0.5           | 5              | 6            | 6                  | 9            | 10                                | 0.075                     | 0.15                      | 0.13                       | 0.06                      | 0.51                      | 0.46                       |
| 07016 063                      | * @ ^ + | A  | 4.7                           | 16                            | 2000          | 0.8           | 8              | 10           | 6                  | 9            | 10                                | 0.075                     | 0.19                      | 0.17                       | 0.08                      | 0.39                      | 0.35                       |
| 07016 064                      | * @ ^ + | A  | 6.8                           | 16                            | 1500          | 1.1           | 11             | 13           | 6                  | 9            | 10                                | 0.075                     | 0.22                      | 0.20                       | 0.09                      | 0.34                      | 0.30                       |
| 07016 065                      | * @ ^ + | B  | 6.8                           | 16                            | 1200          | 1.1           | 11             | 13           | 6                  | 9            | 10                                | 0.085                     | 0.27                      | 0.24                       | 0.11                      | 0.32                      | 0.29                       |
| 07016 066                      | * @ ^ + | A  | 10                            | 16                            | 3000          | 1.6           | 16             | 19           | 6                  | 9            | 10                                | 0.075                     | 0.16                      | 0.14                       | 0.06                      | 0.47                      | 0.43                       |
| 07016 067                      | * @ ^ + | B  | 10                            | 16                            | 900           | 1.6           | 16             | 19           | 6                  | 9            | 10                                | 0.085                     | 0.32                      | 0.29                       | 0.13                      | 0.26                      | 0.23                       |
| 07016 068                      | * @ ^ + | B  | 15                            | 16                            | 800           | 2.4           | 24             | 29           | 6                  | 9            | 10                                | 0.085                     | 0.33                      | 0.29                       | 0.13                      | 0.26                      | 0.23                       |
| 07016 069                      | * @ ^ + | B  | 15                            | 16                            | 500           | 2.4           | 24             | 29           | 6                  | 9            | 10                                | 0.085                     | 0.41                      | 0.37                       | 0.16                      | 0.21                      | 0.19                       |
| 07016 070                      | * @ ^ + | B  | 22                            | 16                            | 600           | 3.6           | 36             | 43           | 6                  | 9            | 10                                | 0.085                     | 0.38                      | 0.34                       | 0.15                      | 0.23                      | 0.20                       |
| 07016 071                      | * @ ^ + | C  | 22                            | 16                            | 375           | 3.6           | 36             | 43           | 6                  | 9            | 10                                | 0.110                     | 0.54                      | 0.49                       | 0.22                      | 0.20                      | 0.18                       |
| 07016 072                      | * @ ^ + | C  | 22                            | 16                            | 150           | 3.6           | 36             | 43           | 6                  | 9            | 10                                | 0.110                     | 0.86                      | 0.77                       | 0.34                      | 0.13                      | 0.12                       |
| 07016 073                      | * @ ^ + | B  | 22                            | 16                            | 500           | 3.6           | 36             | 43           | 6                  | 9            | 10                                | 0.085                     | 0.41                      | 0.37                       | 0.16                      | 0.21                      | 0.19                       |
| 07016 074                      | * @ ^ + | C  | 33                            | 16                            | 300           | 5.3           | 53             | 64           | 6                  | 9            | 10                                | 0.110                     | 0.61                      | 0.54                       | 0.24                      | 0.18                      | 0.16                       |
| 07016 075                      | * @ ^ + | C  | 33                            | 16                            | 100           | 5.3           | 53             | 64           | 6                  | 9            | 10                                | 0.110                     | 1.05                      | 0.94                       | 0.42                      | 0.10                      | 0.09                       |
| 95158 09                       | * ^ A   | D  | 33                            | 16                            | 250           | 4.2           | 25.2           | 42           | 4                  | 6            | 6                                 | 0.150                     | 0.77                      | 0.70                       | 0.31                      | 0.19                      | 0.17                       |
| 07016 076                      | * @ ^ + | C  | 47                            | 16                            | 350           | 7.6           | 76             | 91           | 6                  | 9            | 10                                | 0.110                     | 0.56                      | 0.50                       | 0.22                      | 0.20                      | 0.18                       |
| 07016 077                      | * @ ^ + | C  | 47                            | 16                            | 110           | 7.6           | 76             | 91           | 6                  | 9            | 10                                | 0.110                     | 1.00                      | 0.90                       | 0.40                      | 0.11                      | 0.10                       |
| 07016 078                      | * @ ^ + | D  | 47                            | 16                            | 80            | 7.6           | 76             | 91           | 6                  | 9            | 10                                | 0.150                     | 1.37                      | 1.23                       | 0.55                      | 0.11                      | 0.10                       |
| 95158 10                       | * ^ A   | D  | 47                            | 16                            | 200           | 7.5           | 75             | 94           | 6                  | 9            | 9                                 | 0.150                     | 0.87                      | 0.78                       | 0.35                      | 0.17                      | 0.16                       |
| 07016 079                      | * @ ^ + | D  | 68                            | 16                            | 150           | 10.9          | 109            | 131          | 6                  | 9            | 10                                | 0.150                     | 1.00                      | 0.90                       | 0.40                      | 0.15                      | 0.14                       |
| 07016 080                      | * @ ^ + | D  | 100                           | 16                            | 125           | 16            | 160            | 192          | 6                  | 9            | 10                                | 0.150                     | 1.10                      | 0.99                       | 0.44                      | 0.14                      | 0.12                       |
| 07016 081                      | * @ ^ + | D  | 100                           | 16                            | 50            | 16            | 160            | 192          | 6                  | 9            | 10                                | 0.150                     | 1.73                      | 1.56                       | 0.69                      | 0.09                      | 0.08                       |
| 95158 11                       | * ^ A   | E  | 100                           | 16                            | 125           | 16            | 160            | 200          | 8                  | 12           | 12                                | 0.165                     | 1.15                      | 1.03                       | 0.46                      | 0.14                      | 0.13                       |
| 07016 082                      | M @ ^ + | D  | 150                           | 16                            | 150           | 24            | 240            | 288          | 6                  | 9            | 10                                | 0.150                     | 1.00                      | 0.90                       | 0.40                      | 0.15                      | 0.14                       |
| 07016 083                      | M @ ^ + | D  | 150                           | 16                            | 60            | 24            | 240            | 288          | 6                  | 9            | 10                                | 0.150                     | 1.58                      | 1.42                       | 0.63                      | 0.09                      | 0.09                       |
| 07016 084                      | * @ ^ + | V  | 150                           | 16                            | 45            | 24            | 480            | 288          | 6                  | 8            | 10                                | 0.250                     | 2.36                      | 2.12                       | 0.94                      | 0.11                      | 0.10                       |
| 07016 085                      | * @ ^ + | V  | 220                           | 16                            | 50            | 35.2          | 352            | 422          | 8                  | 10           | 12                                | 0.250                     | 2.24                      | 2.01                       | 0.89                      | 0.11                      | 0.10                       |
| 07016 086                      | * @ ^ + | A  | 1.5                           | 20                            | 6500          | 0.5           | 5              | 6            | 6                  | 8            | 10                                | 0.075                     | 0.11                      | 0.10                       | 0.04                      | 0.70                      | 0.63                       |
| 07016 087                      | * @ ^ + | A  | 2.2                           | 20                            | 3000          | 0.5           | 5              | 6            | 6                  | 8            | 10                                | 0.075                     | 0.16                      | 0.14                       | 0.06                      | 0.47                      | 0.43                       |
| 07016 088                      | * @ ^ + | A  | 4.7                           | 20                            | 4000          | 1             | 10             | 12           | 6                  | 8            | 10                                | 0.075                     | 0.14                      | 0.12                       | 0.05                      | 0.55                      | 0.49                       |
| 07016 089                      | * @ ^ + | A  | 4.7                           | 20                            | 1800          | 1             | 10             | 12           | 6                  | 8            | 10                                | 0.075                     | 0.20                      | 0.18                       | 0.08                      | 0.37                      | 0.33                       |
| 07016 090                      | * @ ^ + | B  | 4.7                           | 20                            | 1000          | 2             | 20             | 24           | 6                  | 8            | 10                                | 0.085                     | 0.29                      | 0.26                       | 0.12                      | 0.29                      | 0.26                       |
| 07016 091                      | * @ ^ + | B  | 6.8                           | 20                            | 1000          | 1.4           | 14             | 17           | 6                  | 8            | 10                                | 0.085                     | 0.29                      | 0.26                       | 0.12                      | 0.29                      | 0.26                       |
| 07016 092                      | * @ ^ + | B  | 10                            | 20                            | 1000          | 0.7           | 7              | 8            | 6                  | 8            | 10                                | 0.085                     | 0.29                      | 0.26                       | 0.12                      | 0.29                      | 0.26                       |
| 07016 093                      | * @ ^ + | B  | 10                            | 20                            | 500           | 0.7           | 7              | 8            | 6                  | 8            | 10                                | 0.085                     | 0.41                      | 0.37                       | 0.16                      | 0.21                      | 0.19                       |
| 07016 094                      | * @ ^ + | C  | 10                            | 20                            | 700           | 1.4           | 14             | 17           | 6                  | 8            | 10                                | 0.110                     | 0.40                      | 0.36                       | 0.16                      | 0.28                      | 0.25                       |
| 07016 095                      | * @ ^ + | B  | 15                            | 20                            | 500           | 3             | 30             | 36           | 6                  | 8            | 10                                | 0.085                     | 0.41                      | 0.37                       | 0.16                      | 0.21                      | 0.19                       |
| 07016 096                      | * @ ^ + | C  | 15                            | 20                            | 450           | 3             | 30             | 36           | 6                  | 8            | 10                                | 0.110                     | 0.49                      | 0.44                       | 0.20                      | 0.22                      | 0.20                       |
| 95158 12                       | * ^ A   | D  | 15                            | 20                            | 275           | 2.4           | 14.4           | 24           | 4                  | 6            | 6                                 | 0.150                     | 0.74                      | 0.66                       | 0.30                      | 0.20                      | 0.18                       |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# DSCC Dwgs 07016 & 95158



## COTS-Plus

| RATING & PART NUMBER REFERENCE |         | Parametric Specifications by Rating per DSCC 95158 or 07016 where applicable |                               |                               |               |               |                |              |                    |              | Typical RMS Ripple Data by Rating |                           |                           |                            |                           |                           |                            |
|--------------------------------|---------|--|-------------------------------|-------------------------------|---------------|---------------|----------------|--------------|--------------------|--------------|-----------------------------------|---------------------------|---------------------------|----------------------------|---------------------------|---------------------------|----------------------------|
|                                |         | Cap @ 120Hz<br>µF @ 25°C   | DC Rated Voltage @ +85°C<br>V | ESR @ 100kHz @ +25°C<br>mOhms | DCL max       |               |                | DF Max       |                    |              | Power Dissipation<br>W            | 25°C Ripple<br>A (100kHz) | 85°C Ripple<br>A (100kHz) | 125°C Ripple<br>A (100kHz) | 25°C Ripple<br>V (100kHz) | 85°C Ripple<br>V (100kHz) | 125°C Ripple<br>V (100kHz) |
|                                |         |  |                               |                               | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +(85/125)°C<br>(%) | -55°C<br>(%) |                                   |                           |                           |                            |                           |                           |                            |
| DSCC P/N                       | Case    |  |                               |                               |               |               |                |              |                    |              |                                   |                           |                           |                            |                           |                           |                            |
| 07016 097                      | * @ ^ + | B  | 22                            | 20                            | 600           | 4.4           | 44             | 53           | 6                  | 8            | 10                                | 0.085                     | 0.38                      | 0.34                       | 0.15                      | 0.20                      | 0.09                       |
| 07016 098                      | * @ ^ + | C  | 22                            | 20                            | 400           | 4.4           | 44             | 53           | 6                  | 8            | 10                                | 0.110                     | 0.52                      | 0.47                       | 0.21                      | 0.19                      | 0.08                       |
| <b>95158 13</b>                | * ^     | D  | 22                            | 20                            | 275           | 3.5           | 21             | 35           | 4                  | 6            | 6                                 | 0.150                     | 0.74                      | 0.66                       | 0.30                      | 0.20                      | 0.18                       |
| 07016 099                      | * @ ^ + | C  | 33                            | 20                            | 300           | 6.6           | 66             | 79           | 6                  | 8            | 10                                | 0.110                     | 0.61                      | 0.54                       | 0.24                      | 0.18                      | 0.16                       |
| 07016 100                      | * @ ^ + | D  | 33                            | 20                            | 200           | 6.6           | 66             | 79           | 6                  | 8            | 10                                | 0.150                     | 0.87                      | 0.78                       | 0.35                      | 0.17                      | 0.16                       |
| 07016 101                      | * @ ^ + | D  | 33                            | 20                            | 100           | 6.6           | 66             | 79           | 6                  | 8            | 10                                | 0.150                     | 1.22                      | 1.10                       | 0.49                      | 0.12                      | 0.11                       |
| 07016 102                      | * @ ^ + | D  | 47                            | 20                            | 200           | 9.4           | 94             | 113          | 6                  | 8            | 10                                | 0.150                     | 0.87                      | 0.78                       | 0.35                      | 0.17                      | 0.16                       |
| 07016 103                      | * @ ^ + | D  | 47                            | 20                            | 100           | 9.4           | 94             | 113          | 6                  | 8            | 10                                | 0.150                     | 1.22                      | 1.10                       | 0.49                      | 0.12                      | 0.11                       |
| <b>95158 14</b>                | * ^     | E  | 47                            | 20                            | 150           | 7.5           | 45             | 75           | 4                  | 6            | 6                                 | 0.165                     | 1.05                      | 0.94                       | 0.42                      | 0.16                      | 0.14                       |
| 07016 104                      | * @ ^ + | D  | 68                            | 20                            | 200           | 13.6          | 136            | 163          | 6                  | 8            | 10                                | 0.150                     | 0.87                      | 0.78                       | 0.35                      | 0.17                      | 0.16                       |
| 07016 105                      | * @ ^ + | D  | 68                            | 20                            | 70            | 13.6          | 136            | 163          | 6                  | 8            | 10                                | 0.150                     | 1.46                      | 1.32                       | 0.59                      | 0.10                      | 0.09                       |
| 07016 106                      | * @ ^ + | E  | 68                            | 20                            | 200           | 13.6          | 136            | 163          | 6                  | 8            | 10                                | 0.165                     | 0.91                      | 0.82                       | 0.36                      | 0.18                      | 0.16                       |
| <b>95158 15</b>                | * ^     | E  | 68                            | 20                            | 150           | 13.6          | 136            | 170          | 6                  | 8            | 9                                 | 0.165                     | 1.05                      | 0.94                       | 0.42                      | 0.16                      | 0.14                       |
| 07016 107                      | * @ ^ + | V  | 100                           | 20                            | 60            | 20            | 200            | 240          | 8                  | 10           | 12                                | 0.250                     | 2.04                      | 1.84                       | 0.82                      | 0.12                      | 0.11                       |
| 07016 108                      | M @ ^ + | A  | 0.7                           | 25                            | 10000         | 0.5           | 5              | 6            | 4                  | 6            | 8                                 | 0.075                     | 0.09                      | 0.08                       | 0.03                      | 0.87                      | 0.78                       |
| 07016 109                      | * @ ^ + | A  | 1.0                           | 25                            | 8000          | 0.5           | 5              | 6            | 4                  | 6            | 8                                 | 0.075                     | 0.10                      | 0.09                       | 0.04                      | 0.77                      | 0.70                       |
| 07016 110                      | * @ ^ + | A  | 1.5                           | 25                            | 7500          | 0.5           | 5              | 6            | 6                  | 8            | 10                                | 0.075                     | 0.10                      | 0.09                       | 0.04                      | 0.75                      | 0.68                       |
| 07016 111                      | * @ ^ + | A  | 1.5                           | 25                            | 3000          | 0.5           | 5              | 6            | 6                  | 8            | 10                                | 0.075                     | 0.16                      | 0.14                       | 0.06                      | 0.47                      | 0.43                       |
| 07016 112                      | * @ ^ + | A  | 2.2                           | 25                            | 7000          | 0.5           | 5              | 6            | 6                  | 8            | 10                                | 0.075                     | 0.10                      | 0.09                       | 0.04                      | 0.72                      | 0.65                       |
| 07016 113                      | * @ ^ + | B  | 2.2                           | 25                            | 2000          | 0.5           | 5              | 6            | 6                  | 8            | 10                                | 0.085                     | 0.21                      | 0.19                       | 0.08                      | 0.41                      | 0.37                       |
| 07016 114                      | * @ ^ + | B  | 3.3                           | 25                            | 2000          | 0.5           | 5              | 6            | 6                  | 8            | 10                                | 0.085                     | 0.21                      | 0.19                       | 0.08                      | 0.41                      | 0.37                       |
| 07016 115                      | * @ ^ + | A  | 4.7                           | 25                            | 3100          | 1.2           | 12             | 14           | 6                  | 9            | 10                                | 0.075                     | 0.16                      | 0.14                       | 0.06                      | 0.48                      | 0.43                       |
| 07016 116                      | * @ ^ + | B  | 4.7                           | 25                            | 1500          | 1.2           | 12             | 14           | 6                  | 8            | 10                                | 0.085                     | 0.24                      | 0.21                       | 0.10                      | 0.36                      | 0.32                       |
| 07016 117                      | * @ ^ + | B  | 4.7                           | 25                            | 700           | 1.2           | 12             | 14           | 6                  | 8            | 10                                | 0.085                     | 0.35                      | 0.31                       | 0.14                      | 0.24                      | 0.22                       |
| 07016 118                      | * @ ^ + | B  | 6.8                           | 25                            | 2800          | 1.7           | 17             | 20           | 6                  | 8            | 10                                | 0.085                     | 0.17                      | 0.16                       | 0.07                      | 0.49                      | 0.44                       |
| 07016 119                      | * @ ^ + | B  | 6.8                           | 25                            | 700           | 1.7           | 17             | 20           | 6                  | 8            | 10                                | 0.085                     | 0.35                      | 0.31                       | 0.14                      | 0.24                      | 0.22                       |
| 07016 120                      | * @ ^ + | C  | 6.8                           | 25                            | 700           | 1.7           | 17             | 20           | 6                  | 8            | 10                                | 0.110                     | 0.40                      | 0.36                       | 0.16                      | 0.28                      | 0.25                       |
| 07016 121                      | * @ ^ + | C  | 10                            | 25                            | 500           | 2.5           | 25             | 30           | 6                  | 8            | 10                                | 0.110                     | 0.47                      | 0.42                       | 0.19                      | 0.23                      | 0.21                       |
| 07016 122                      | * @ ^ + | C  | 10                            | 25                            | 300           | 2.5           | 25             | 30           | 6                  | 8            | 10                                | 0.110                     | 0.61                      | 0.54                       | 0.24                      | 0.18                      | 0.16                       |
| <b>95158 16</b>                | * ^     | D  | 15                            | 25                            | 275           | 3.8           | 38             | 46.9         | 6                  | 9            | 9                                 | 0.150                     | 0.74                      | 0.66                       | 0.30                      | 0.20                      | 0.18                       |
| <b>95158 17</b>                | * ^     | E  | 15                            | 25                            | 200           | 3             | 18             | 30           | 4                  | 6            | 6                                 | 0.165                     | 0.91                      | 0.82                       | 0.36                      | 0.18                      | 0.16                       |
| 07016 123                      | * @ ^ + | C  | 22                            | 25                            | 400           | 5.5           | 55             | 66           | 6                  | 8            | 10                                | 0.110                     | 0.52                      | 0.47                       | 0.21                      | 0.21                      | 0.19                       |
| 07016 124                      | * @ ^ + | C  | 22                            | 25                            | 275           | 5.5           | 55             | 66           | 6                  | 8            | 10                                | 0.110                     | 0.63                      | 0.57                       | 0.25                      | 0.17                      | 0.16                       |
| 07016 125                      | * @ ^ + | D  | 22                            | 25                            | 200           | 5.5           | 55             | 66           | 6                  | 8            | 10                                | 0.150                     | 0.87                      | 0.78                       | 0.35                      | 0.17                      | 0.16                       |
| 07016 126                      | * @ ^ + | D  | 22                            | 25                            | 100           | 5.5           | 55             | 66           | 6                  | 8            | 10                                | 0.150                     | 1.22                      | 1.10                       | 0.49                      | 0.12                      | 0.11                       |
| <b>95158 18</b>                | * ^     | E  | 22                            | 25                            | 225           | 4.4           | 26.4           | 44           | 4                  | 6            | 6                                 | 0.165                     | 0.86                      | 0.77                       | 0.34                      | 0.19                      | 0.17                       |
| 07016 127                      | * @ ^ + | D  | 33                            | 25                            | 300           | 8.3           | 83             | 100          | 6                  | 8            | 10                                | 0.150                     | 0.71                      | 0.64                       | 0.28                      | 0.21                      | 0.19                       |
| 07016 128                      | * @ ^ + | D  | 33                            | 25                            | 90            | 8.3           | 83             | 100          | 6                  | 8            | 10                                | 0.150                     | 1.22                      | 1.10                       | 0.49                      | 0.12                      | 0.11                       |
| <b>95158 19</b>                | * ^     | E  | 33                            | 25                            | 175           | 6.6           | 39.6           | 66           | 4                  | 6            | 6                                 | 0.165                     | 0.97                      | 0.87                       | 0.39                      | 0.17                      | 0.15                       |
| 07016 129                      | * @ ^ + | E  | 33                            | 25                            | 100           | 8.3           | 83             | 100          | 6                  | 8            | 10                                | 0.165                     | 1.35                      | 1.22                       | 0.54                      | 0.12                      | 0.11                       |
| 07016 130                      | M @ ^ + | D  | 47                            | 25                            | 250           | 11.8          | 118            | 142          | 6                  | 8            | 10                                | 0.150                     | 0.77                      | 0.70                       | 0.31                      | 0.19                      | 0.17                       |
| 07016 131                      | M @ ^ + | D  | 47                            | 25                            | 175           | 11.8          | 118            | 142          | 6                  | 8            | 10                                | 0.150                     | 0.93                      | 0.83                       | 0.37                      | 0.16                      | 0.15                       |
| 07016 132                      | * @ ^ + | V  | 68                            | 25                            | 95            | 17            | 170            | 204          | 8                  | 10           | 12                                | 0.250                     | 1.62                      | 1.46                       | 0.65                      | 0.15                      | 0.14                       |
| 07016 133                      | M @ ^ + | A  | 0.47                          | 35                            | 12000         | 0.5           | 5              | 6            | 4                  | 6            | 8                                 | 0.075                     | 0.08                      | 0.07                       | 0.03                      | 0.95                      | 0.85                       |
| 07016 134                      | M @ ^ + | A  | 0.68                          | 35                            | 8000          | 0.5           | 5              | 6            | 4                  | 6            | 8                                 | 0.075                     | 0.10                      | 0.09                       | 0.04                      | 0.77                      | 0.70                       |
| 07016 135                      | * @ ^ + | A  | 1.0                           | 35                            | 7500          | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.075                     | 0.10                      | 0.09                       | 0.04                      | 0.75                      | 0.68                       |
| 07016 136                      | * @ ^ + | A  | 1.5                           | 35                            | 7500          | 0.5           | 5              | 6            | 6                  | 8            | 9                                 | 0.075                     | 0.10                      | 0.09                       | 0.04                      | 0.75                      | 0.68                       |
| 07016 137                      | * @ ^ + | B  | 1.5                           | 35                            | 5200          | 0.5           | 5              | 6            | 6                  | 8            | 9                                 | 0.085                     | 0.13                      | 0.12                       | 0.05                      | 0.66                      | 0.60                       |
| 07016 138                      | * @ ^ + | B  | 2.2                           | 35                            | 2000          | 0.8           | 8              | 10           | 6                  | 8            | 9                                 | 0.085                     | 0.21                      | 0.19                       | 0.08                      | 0.41                      | 0.37                       |
| 07016 139                      | * @ ^ + | B  | 3.3                           | 35                            | 1000          | 1.2           | 12             | 14           | 6                  | 8            | 9                                 | 0.085                     | 0.29                      | 0.26                       | 0.12                      | 0.29                      | 0.26                       |
| 07016 140                      | * @ ^ + | B  | 4.7                           | 35                            | 1500          | 1.6           | 16             | 19           | 6                  | 8            | 9                                 | 0.085                     | 0.24                      | 0.21                       | 0.10                      | 0.36                      | 0.32                       |
| <b>95158 29</b>                | * ^     | C  | 4.7                           | 35                            | 600           | 1.7           | 10.2           | 17           | 6                  | 8            | 9                                 | 0.110                     | 0.43                      | 0.39                       | 0.17                      | 0.26                      | 0.23                       |
| 07016 141                      | * @ ^ + | D  | 4.7                           | 35                            | 450           | 1.6           | 16             | 20           | 6                  | 8            | 9                                 | 0.110                     | 0.49                      | 0.44                       | 0.20                      | 0.22                      | 0.20                       |
| 07016 142                      | * @ ^ + | C  | 6.8                           | 35                            | 350           | 2.4           | 24             | 29           | 6                  | 9            | 9                                 | 0.150                     | 0.65                      | 0.59                       | 0.26                      | 0.23                      | 0.21                       |
| 07016 143                      | * @ ^ + | D  | 6.8                           | 35                            | 400           | 2.4           | 24             | 29           | 6                  | 9            | 9                                 | 0.165                     | 0.64                      | 0.58                       | 0.26                      | 0.26                      | 0.23                       |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# DSCC Dwgs 07016 & 95158



## COTS-Plus

| RATING & PART NUMBER REFERENCE |         | Parametric Specifications by Rating per DSCC 95158 or 07016 where applicable |                               |                               |               |               |                |              |                    |              | Typical RMS Ripple Data by Rating |                           |                           |                            |                           |                           |                            |      |
|--------------------------------|---------|--|-------------------------------|-------------------------------|---------------|---------------|----------------|--------------|--------------------|--------------|-----------------------------------|---------------------------|---------------------------|----------------------------|---------------------------|---------------------------|----------------------------|------|
|                                |         | Cap @ 120Hz<br>µF @ 25°C   | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>mOhms @ +25°C | DCL max       |               |                | DF Max       |                    |              | Power Dissipation<br>W            | 25°C Ripple<br>A (100kHz) | 85°C Ripple<br>A (100kHz) | 125°C Ripple<br>A (100kHz) | 25°C Ripple<br>V (100kHz) | 85°C Ripple<br>V (100kHz) | 125°C Ripple<br>V (100kHz) |      |
|                                |         |  |                               |                               | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +(85/125)°C<br>(%) | -55°C<br>(%) |                                   |                           |                           |                            |                           |                           |                            |      |
| DSCC P/N                       | Case    |  |                               |                               |               |               |                |              |                    |              |                                   |                           |                           |                            |                           |                           |                            |      |
| 95158 20                       | * ^ ^   | E  | 6.8                           | 35                            | 300           | 1.9           | 11.4           | 19           | 4                  | 6            | 6                                 | 0.165                     | 0.74                      | 0.67                       | 0.30                      | 0.22                      | 0.20                       | 0.09 |
| 07016 144                      | * @ ^ + | C  | 10                            | 35                            | 1600          | 3.5           | 35             | 42           | 6                  | 9            | 9                                 | 0.110                     | 0.26                      | 0.24                       | 0.10                      | 0.42                      | 0.38                       | 0.17 |
| 95158 27                       | * ^ ^   | D  | 10                            | 35                            | 300           | 3.5           | 35             | 42           | 4                  | 6            | 6                                 | 0.150                     | 0.71                      | 0.64                       | 0.28                      | 0.21                      | 0.19                       | 0.08 |
| 07016 145                      | * @ ^ + | D  | 10                            | 35                            | 125           | 3.5           | 35             | 42           | 6                  | 9            | 9                                 | 0.150                     | 1.10                      | 0.99                       | 0.44                      | 0.14                      | 0.12                       | 0.05 |
| 95158 21                       | * ^ ^   | E  | 10                            | 35                            | 250           | 2.8           | 16.8           | 28           | 4                  | 6            | 6                                 | 0.165                     | 0.81                      | 0.73                       | 0.32                      | 0.20                      | 0.18                       | 0.08 |
| 07016 146                      | * @ ^ + | C  | 15                            | 35                            | 450           | 5.3           | 53             | 64           | 6                  | 9            | 9                                 | 0.110                     | 0.49                      | 0.44                       | 0.20                      | 0.22                      | 0.20                       | 0.09 |
| 07016 147                      | * @ ^ + | D  | 15                            | 35                            | 300           | 5.3           | 53             | 64           | 6                  | 9            | 9                                 | 0.150                     | 0.71                      | 0.64                       | 0.28                      | 0.21                      | 0.19                       | 0.08 |
| 07016 148                      | * @ ^ + | D  | 15                            | 35                            | 100           | 5.3           | 53             | 64           | 6                  | 9            | 9                                 | 0.150                     | 1.22                      | 1.10                       | 0.49                      | 0.12                      | 0.11                       | 0.05 |
| 95158 22                       | * ^ ^   | E  | 15                            | 35                            | 225           | 5.3           | 53             | 65.6         | 6                  | 9            | 9                                 | 0.165                     | 0.86                      | 0.77                       | 0.34                      | 0.19                      | 0.17                       | 0.08 |
| 07016 149                      | * @ ^ + | D  | 22                            | 35                            | 400           | 7.7           | 77             | 92           | 6                  | 9            | 9                                 | 0.150                     | 0.61                      | 0.55                       | 0.24                      | 0.24                      | 0.22                       | 0.10 |
| 07016 150                      | * @ ^ + | D  | 22                            | 35                            | 125           | 7.7           | 77             | 92           | 6                  | 9            | 9                                 | 0.150                     | 1.10                      | 0.99                       | 0.44                      | 0.14                      | 0.12                       | 0.05 |
| 95158 23                       | * ^ ^   | E  | 22                            | 35                            | 300           | 7.7           | 77             | 96.3         | 6                  | 9            | 9                                 | 0.165                     | 0.74                      | 0.67                       | 0.30                      | 0.22                      | 0.20                       | 0.09 |
| 07016 151                      | * @ ^ + | E  | 22                            | 35                            | 125           | 7.7           | 77             | 92           | 6                  | 9            | 9                                 | 0.165                     | 1.15                      | 1.03                       | 0.46                      | 0.14                      | 0.13                       | 0.06 |
| 07016 152                      | M @ ^ + | D  | 33                            | 35                            | 300           | 11.6          | 116            | 139          | 6                  | 9            | 9                                 | 0.150                     | 0.71                      | 0.64                       | 0.28                      | 0.21                      | 0.19                       | 0.08 |
| 07016 153                      | M @ ^ + | D  | 33                            | 35                            | 200           | 11.6          | 116            | 139          | 6                  | 9            | 9                                 | 0.150                     | 0.87                      | 0.78                       | 0.35                      | 0.17                      | 0.16                       | 0.07 |
| 07016 154                      | M @ ^ + | E  | 33                            | 35                            | 300           | 11.6          | 116            | 139          | 6                  | 9            | 9                                 | 0.165                     | 0.74                      | 0.67                       | 0.30                      | 0.22                      | 0.20                       | 0.09 |
| 07016 155                      | M @ ^ + | E  | 47                            | 35                            | 250           | 16.5          | 165            | 197          | 6                  | 9            | 9                                 | 0.165                     | 0.81                      | 0.73                       | 0.32                      | 0.20                      | 0.18                       | 0.08 |
| 07016 156                      | M @ ^ + | V  | 47                            | 35                            | 200           | 16.5          | 165            | 197          | 6                  | 9            | 9                                 | 0.250                     | 1.12                      | 1.01                       | 0.45                      | 0.22                      | 0.20                       | 0.09 |
| 07016 157                      | M @ ^ + | A  | 0.15                          | 50                            | 15000         | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.075                     | 0.07                      | 0.06                       | 0.03                      | 1.06                      | 0.95                       | 0.42 |
| 07016 158                      | M @ ^ + | A  | 0.22                          | 50                            | 18000         | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.075                     | 0.06                      | 0.06                       | 0.03                      | 1.16                      | 1.05                       | 0.46 |
| 07016 159                      | * @ ^ + | A  | 0.47                          | 50                            | 9500          | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.075                     | 0.09                      | 0.08                       | 0.04                      | 0.84                      | 0.76                       | 0.34 |
| 07016 160                      | * @ ^ + | B  | 0.47                          | 50                            | 9500          | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.085                     | 0.09                      | 0.09                       | 0.04                      | 0.90                      | 0.81                       | 0.36 |
| 07016 161                      | * @ ^ + | A  | 0.68                          | 50                            | 7900          | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.075                     | 0.10                      | 0.09                       | 0.04                      | 0.77                      | 0.69                       | 0.31 |
| 07016 162                      | M @ ^ + | A  | 1.0                           | 50                            | 6600          | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.075                     | 0.11                      | 0.10                       | 0.04                      | 0.70                      | 0.63                       | 0.28 |
| 07016 163                      | * @ ^ + | B  | 1.0                           | 50                            | 7000          | 0.5           | 5              | 6            | 4                  | 6            | 6                                 | 0.085                     | 0.11                      | 0.10                       | 0.04                      | 0.77                      | 0.69                       | 0.31 |
| 07016 164                      | * @ ^ + | C  | 1.5                           | 50                            | 2000          | 0.8           | 8              | 10           | 6                  | 8            | 9                                 | 0.110                     | 0.23                      | 0.21                       | 0.09                      | 0.47                      | 0.42                       | 0.19 |
| 07016 165                      | * @ ^ + | D  | 1.5                           | 50                            | 1500          | 0.8           | 8              | 10           | 6                  | 8            | 9                                 | 0.150                     | 0.32                      | 0.28                       | 0.13                      | 0.47                      | 0.43                       | 0.19 |
| 07016 166                      | * @ ^ + | D  | 2.2                           | 50                            | 1200          | 1.1           | 11             | 13           | 6                  | 8            | 9                                 | 0.150                     | 0.35                      | 0.32                       | 0.14                      | 0.42                      | 0.38                       | 0.17 |
| 07016 167                      | * @ ^ + | D  | 3.3                           | 50                            | 800           | 1.7           | 17             | 20           | 6                  | 9            | 9                                 | 0.150                     | 0.43                      | 0.39                       | 0.17                      | 0.35                      | 0.31                       | 0.14 |
| 07016 168                      | * @ ^ + | D  | 4.7                           | 50                            | 300           | 2.4           | 24             | 29           | 6                  | 9            | 9                                 | 0.150                     | 0.71                      | 0.64                       | 0.28                      | 0.21                      | 0.19                       | 0.08 |
| 07016 169                      | * @ ^ + | D  | 6.8                           | 50                            | 600           | 3.4           | 34             | 41           | 6                  | 6            | 6                                 | 0.150                     | 0.50                      | 0.45                       | 0.20                      | 0.30                      | 0.27                       | 0.12 |
| 07016 170                      | * @ ^ + | D  | 6.8                           | 50                            | 300           | 3.4           | 34             | 41           | 6                  | 6            | 6                                 | 0.150                     | 0.71                      | 0.64                       | 0.28                      | 0.21                      | 0.19                       | 0.08 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# T4J – Medical Series



## HRC4000 Implantable Non Life Support and Non Implantable Life Support



The AVX T4J series is designed for use in Implantable - Non-Life support or Non-Implantable - Life support medical applications. These components are screened using our newly designed Q-Process to effectively remove components that may experience parametric shifts through customer processing or display instability through life testing.



For RoHS compliant products, please select correct termination style.



### FEATURES

- Dedicated to medical applications
- HRC4000 - Implantable, Non-Life support  
- Non-Implantable, Life support
- -55 to +125°C operation temperature
- Basic reliability better than 0.1%/1000hours
- Custom DCL / ESR options on selected parts


**T4J Standard** – Standard option DCL and ESR limits including Q-Process screening.

**T4J Custom** – A custom option where specific DCL and ESR parameter limits can be agreed based Q-Process statistical screening. DCL down to 0.005CV on selected codes

### APPLICATIONS


- Medical, Implantable - Non-Life support and Non-Implantable - Life support

For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)



### MARKING

A, B, C, D, E, U, V CASE



### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|------------|----------------|------------------------------|------------------------------|------------------------------|------------------------------|--------------|
| A    | 1206     | 3216-18    | 3.20 (0.126)   | 1.60 (0.063)                 | 1.60 (0.063)                 | 1.20 (0.047)                 | 0.80 (0.031)                 | 1.10 (0.043) |
| B    | 1210     | 3528-21    | 3.50 (0.138)   | 2.80 (0.110)                 | 1.90 (0.075)                 | 2.20 (0.087)                 | 0.80 (0.031)                 | 1.40 (0.055) |
| C    | 2312     | 6032-28    | 6.00 (0.236)   | 3.20 (0.126)                 | 2.60 (0.102)                 | 2.20 (0.087)                 | 1.30 (0.051)                 | 2.90 (0.114) |
| D    | 2917     | 7343-31    | 7.30 (0.287)   | 4.30 (0.169)                 | 2.90 (0.114)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| E    | 2917     | 7343-43    | 7.30 (0.287)   | 4.30 (0.169)                 | 4.10 (0.162)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| U    | 2924     | 7361-43    | 7.30 (0.287)   | 6.10 (0.240)                 | 4.10 (0.162)                 | 3.10 (0.120)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| V    | 2924     | 7361-38    | 7.30 (0.287)   | 6.10 (0.240)                 | 3.55 (0.140)                 | 3.10 (0.120)                 | 1.30 (0.051)                 | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### HOW TO ORDER

| T4J  | E                            | 336   | K                     | 035  | C   | □                                    | L                                      | Q  | 4                                  | ^  | 00                                     |
|------|------------------------------|---|-----------------------|--|---|--------------------------------------|--|--|------------------------------------|--|--|
| Type | Case Size<br>See table above | Capacitance Code<br>pF code:<br>1st two digits represent significant figures<br>3rd digit represents multiplier (number of zeros to follow) | Tolerance<br>K = ±10% | Rated DC Voltage<br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | Standard or Low ESR Range<br>C = Std ESR<br>L = Low ESR | Packaging<br>R = 7" Reel<br>B = Bulk | Inspection Level<br>L = Lab Inspection | Reliability Grade<br>Q = Q-Process Screening | Qualification Level<br>4 = HCR4000 | Termination<br>7 = 100% Tin<br>9 = Gold Plated<br>H = SnPb Non RoHS<br>H,9 = (Contact Manufacturer) Non RoHS | Suffix<br>00 = Standard<br>XX = Custom |

### TECHNICAL SPECIFICATIONS

|                                    |   |     |    |    |    |    |    |    |  |
|------------------------------------|---|-----|----|----|----|----|----|----|--|
| Technical Data:                    | All technical data relate to an ambient temperature of +25°C                  |     |    |    |    |    |    |    |  |
| Capacitance Range:                 | 1 µF to 1000 µF   |     |    |    |    |    |    |    |  |
| Capacitance Tolerance:             | ±10%  |     |    |    |    |    |    |    |  |
| Leakage Current DCL:               | 0.01CV (Custom potential down to 0.005CV available upon request)              |     |    |    |    |    |    |    |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 6.3 | 10 | 16 | 20 | 25 | 35 | 50 |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 4   | 7  | 10 | 13 | 17 | 23 | 33 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 8   | 13 | 20 | 26 | 32 | 46 | 65 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 5   | 8  | 13 | 16 | 20 | 28 | 40 |  |
| Temperature Range:                 | -55°C to +125°C   |     |    |    |    |    |    |    |  |
| Reliability:                       | 0.1% / 1000hrs at 25°C, VR with 0.1Ω/V series impedance, 90% confidence level |     |    |    |    |    |    |    |  |

# T4J – Medical Series



## HRC4000 Implantable Non Life Support and Non Implantable Life Support

### CAPACITANCE AND RATED VOLTAGE, $V_R$ (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance   |      | Rated Voltage DC ( $V_R$ ) to 85°C (Voltage Code) |         |         |        |        |        |         |
|---------------|------|---|---------|---------|--------|--------|--------|---------|
| $\mu\text{F}$ | Code | 6.3V (J)  | 10V (A) | 16V (C) | 20 (D) | 25 (E) | 35 (V) | 50V (T) |
| 1.0           | 105  |   |         |         |        |        | A      | C       |
| 1.5           | 155  |   |         |         |        | A      | B      | C       |
| 2.2           | 225  |   |         |         |        | B      | B      | C       |
| 3.3           | 335  |   |         |         |        | B      | B      | C       |
| 4.7           | 475  |   |         |         | B      | B      | C      | D       |
| 6.8           | 685  |   | A       | B       | B      | C      | C      | D       |
| 10            | 106  | A   | A       | B       | B/C    | C      | C      | E       |
| 15            | 156  | A   | B       | B       | C      | C      | D      |         |
| 22            | 226  | B   | B       | C       | C      | D      | D      |         |
| 33            | 336  | B   | C       | C       | D      | D      | E      |         |
| 47            | 476  | B/C   | C       | D       | D      | D      |        |         |
| 68            | 686  | B/C   | C       | D       | E      |        | V      |         |
| 100           | 107  | B/C   | D       | E       | E      |        |        |         |
| 150           | 157  | D   | D       | E       |        |        |        |         |
| 220           | 227  | D   | E       | U       |        |        |        |         |
| 330           | 337  | E   | E       |         |        |        |        |         |
| 470           | 477  | E   | U       |         |        |        |        |         |
| 680           | 687  | U   |         |         |        |        |        |         |
| 1000          | 108  | V   |         |         |        |        |        |         |

#### Available Ratings

Please contact the factory for codes not listed in the table.

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards with customer written approval.



# T4J – Medical Series



HRC4000 Implantable Non Life Support and Non Implantable Life Support

## RATINGS & PART NUMBER REFERENCE

| AVX Part No.           | Case Size | Capacitance (µF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (µA) | DF Max. (%) | ESR Max. @ 100kHz (mΩ) | MSL | 100kHz RMS Current (mA) |      |       |
|------------------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|------------------------|-----|-------------------------|------|-------|
|                        |           |                  |                   |                        |                      |                           |               |             |                        |     | 25°C                    | 85°C | 125°C |
| <b>6.3 Volt @ 85°C</b> |           |                  |                   |                        |                      |                           |               |             |                        |     |                         |      |       |
| T4JA106K006C□LQ4^00    | A         | 10               | 6.3               | 85                     | 4                    | 125                       | 0.6           | 6           | 1500                   | 3   | 224                     | 201  | 89    |
| T4JA156K006C□LQ4^00    | A         | 15               | 6.3               | 85                     | 4                    | 125                       | 0.9           | 6           | 1500                   | 3   | 224                     | 201  | 89    |
| T4JB226K006C□LQ4^00    | B         | 22               | 6.3               | 85                     | 4                    | 125                       | 1.4           | 6           | 600                    | 3   | 376                     | 339  | 151   |
| T4JB336K006C□LQ4^00    | B         | 33               | 6.3               | 85                     | 4                    | 125                       | 2.1           | 6           | 600                    | 3   | 376                     | 339  | 151   |
| T4JB476K006C□LQ4^00    | B         | 47               | 6.3               | 85                     | 4                    | 125                       | 2.8           | 8           | 1500                   | 3   | 238                     | 214  | 95    |
| T4JC476K006C□LQ4^00    | C         | 47               | 6.3               | 85                     | 4                    | 125                       | 3.0           | 6           | 300                    | 3   | 606                     | 545  | 242   |
| T4JB686K006C□LQ4^00    | B         | 68               | 6.3               | 85                     | 4                    | 125                       | 4.0           | 8           | 900                    | 3   | 307                     | 277  | 123   |
| T4JC686K006C□LQ4^00    | C         | 68               | 6.3               | 85                     | 4                    | 125                       | 4.3           | 6           | 300                    | 3   | 606                     | 545  | 242   |
| T4JB107K006C□LQ4^00    | B         | 100              | 6.3               | 85                     | 4                    | 125                       | 3.0           | 10          | 1400                   | 3   | 246                     | 222  | 99    |
| T4JC107K006C□LQ4^00    | C         | 100              | 6.3               | 85                     | 4                    | 125                       | 6.3           | 6           | 300                    | 3   | 606                     | 545  | 242   |
| T4JD157K006C□LQ4^00    | D         | 150              | 6.3               | 85                     | 4                    | 125                       | 9.5           | 6           | 200                    | 3   | 866                     | 779  | 346   |
| T4JD227K006C□LQ4^00    | D         | 220              | 6.3               | 85                     | 4                    | 125                       | 13.9          | 8           | 200                    | 3   | 866                     | 779  | 346   |
| T4JE337K006C□LQ4^00    | E         | 330              | 6.3               | 85                     | 4                    | 125                       | 20.8          | 8           | 200                    | 3   | 908                     | 817  | 363   |
| T4JE477K006C□LQ4^00    | E         | 470              | 6.3               | 85                     | 4                    | 125                       | 29.6          | 8           | 200                    | 3   | 908                     | 817  | 363   |
| T4JU687K006C□LQ4^00    | U         | 680              | 6.3               | 85                     | 4                    | 125                       | 42.8          | 12          | 250                    | 3   | 812                     | 731  | 325   |
| T4JV108K006C□LQ4^00    | V         | 1000             | 6.3               | 85                     | 4                    | 125                       | 60.0          | 16          | 200                    | 3   | 1118                    | 1006 | 447   |
| <b>10 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |     |                         |      |       |
| T4JA685K010C□LQ4^00    | A         | 6.8              | 10                | 85                     | 7                    | 125                       | 0.7           | 6           | 2000                   | 3   | 194                     | 174  | 77    |
| T4JA106K010C□LQ4^00    | A         | 10               | 10                | 85                     | 7                    | 125                       | 1             | 6           | 2000                   | 3   | 194                     | 174  | 77    |
| T4JB156K010C□LQ4^00    | B         | 15               | 10                | 85                     | 7                    | 125                       | 1.5           | 6           | 700                    | 3   | 348                     | 314  | 139   |
| T4JB226K010C□LQ4^00    | B         | 22               | 10                | 85                     | 7                    | 125                       | 2.2           | 6           | 700                    | 3   | 348                     | 314  | 139   |
| T4JC336K010C□LQ4^00    | C         | 33               | 10                | 85                     | 7                    | 125                       | 3.3           | 6           | 300                    | 3   | 606                     | 545  | 242   |
| T4JC476K010C□LQ4^00    | C         | 47               | 10                | 85                     | 7                    | 125                       | 4.7           | 6           | 300                    | 3   | 606                     | 545  | 242   |
| T4JC686K010C□LQ4^00    | C         | 68               | 10                | 85                     | 7                    | 125                       | 6.8           | 6           | 300                    | 3   | 606                     | 545  | 242   |
| T4JD107K010C□LQ4^00    | D         | 100              | 10                | 85                     | 7                    | 125                       | 10.0          | 6           | 150                    | 3   | 1000                    | 900  | 400   |
| T4JD157K010C□LQ4^00    | D         | 150              | 10                | 85                     | 7                    | 125                       | 15.0          | 8           | 150                    | 3   | 1000                    | 900  | 400   |
| T4JE227K010C□LQ4^00    | E         | 220              | 10                | 85                     | 7                    | 125                       | 22.0          | 8           | 150                    | 3   | 1049                    | 944  | 420   |
| T4JE337K010C□LQ4^00    | E         | 330              | 10                | 85                     | 7                    | 125                       | 33.0          | 8           | 150                    | 3   | 1049                    | 944  | 420   |
| T4JU477K010C□LQ4^00    | U         | 470              | 10                | 85                     | 7                    | 125                       | 47.0          | 12          | 200                    | 3   | 908                     | 817  | 363   |
| <b>16 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |     |                         |      |       |
| T4JB685K016C□LQ4^00    | B         | 6.8              | 16                | 85                     | 10                   | 125                       | 1.1           | 6           | 1200                   | 3   | 266                     | 240  | 106   |
| T4JB106K016C□LQ4^00    | B         | 10               | 16                | 85                     | 10                   | 125                       | 1.6           | 6           | 1200                   | 3   | 266                     | 240  | 106   |
| T4JB156K016C□LQ4^00    | B         | 15               | 16                | 85                     | 10                   | 125                       | 2.4           | 6           | 1200                   | 3   | 266                     | 240  | 106   |
| T4JC226K016C□LQ4^00    | C         | 22               | 16                | 85                     | 10                   | 125                       | 3.5           | 6           | 350                    | 3   | 561                     | 505  | 224   |
| T4JC336K016C□LQ4^00    | C         | 33               | 16                | 85                     | 10                   | 125                       | 5.3           | 6           | 350                    | 3   | 561                     | 505  | 224   |
| T4JD476K016C□LQ4^00    | D         | 47               | 16                | 85                     | 10                   | 125                       | 7.5           | 6           | 200                    | 3   | 866                     | 779  | 346   |
| T4JD686K016C□LQ4^00    | D         | 68               | 16                | 85                     | 10                   | 125                       | 10.9          | 6           | 200                    | 3   | 866                     | 779  | 346   |
| T4JE107K016C□LQ4^00    | E         | 100              | 16                | 85                     | 10                   | 125                       | 16.0          | 6           | 150                    | 3   | 1049                    | 944  | 420   |
| T4JE157K016C□LQ4^00    | E         | 150              | 16                | 85                     | 10                   | 125                       | 24.0          | 6           | 150                    | 3   | 1049                    | 944  | 420   |
| T4JU227K016C□LQ4^00    | U         | 220              | 16                | 85                     | 10                   | 125                       | 35.2          | 12          | 200                    | 3   | 908                     | 817  | 363   |
| <b>20 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |     |                         |      |       |
| T4JB475K020C□LQ4^00    | B         | 4.7              | 20                | 85                     | 13                   | 125                       | 1.0           | 6           | 1000                   | 3   | 292                     | 262  | 117   |
| T4JB685K020C□LQ4^00    | B         | 6.8              | 20                | 85                     | 13                   | 125                       | 1.4           | 6           | 1000                   | 3   | 292                     | 262  | 117   |
| T4JB106K020C□LQ4^00    | B         | 10               | 20                | 85                     | 13                   | 125                       | 1.0           | 6           | 1000                   | 3   | 292                     | 262  | 117   |
| T4JB106K020L□LQ4^00    | B         | 10               | 20                | 85                     | 13                   | 125                       | 1.0           | 6           | 500                    | 3   | 412                     | 371  | 165   |
| T4JC106K020C□LQ4^00    | C         | 10               | 20                | 85                     | 13                   | 125                       | 2.0           | 6           | 500                    | 3   | 469                     | 422  | 188   |
| T4JC156K020C□LQ4^00    | C         | 15               | 20                | 85                     | 13                   | 125                       | 3.0           | 6           | 500                    | 3   | 469                     | 422  | 188   |
| T4JC226K020C□LQ4^00    | C         | 22               | 20                | 85                     | 13                   | 125                       | 4.4           | 6           | 500                    | 3   | 469                     | 422  | 188   |
| T4JD336K020C□LQ4^00    | D         | 33               | 20                | 85                     | 13                   | 125                       | 6.6           | 6           | 250                    | 3   | 775                     | 697  | 310   |
| T4JD476K020C□LQ4^00    | D         | 47               | 20                | 85                     | 13                   | 125                       | 9.4           | 6           | 250                    | 3   | 775                     | 697  | 310   |
| T4JE686K020C□LQ4^00    | E         | 68               | 20                | 85                     | 13                   | 125                       | 13.6          | 6           | 200                    | 3   | 908                     | 817  | 363   |
| T4JE107K020C□LQ4^00    | E         | 100              | 20                | 85                     | 13                   | 125                       | 20.0          | 6           | 200                    | 3   | 908                     | 817  | 363   |

# T4J – Medical Series



## HRC4000 Implantable Non Life Support and Non Implantable Life Support

| AVX Part No.          | Case Size | Capacitance (µF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (µA) | DF Max. (%) | ESR Max. @ 100kHz (mΩ) | MSL | 100kHz RMS Current (mA) |      |       |
|-----------------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|------------------------|-----|-------------------------|------|-------|
|                       |           |                  |                   |                        |                      |                           |               |             |                        |     | 25°C                    | 85°C | 125°C |
| <b>25 Volt @ 85°C</b> |           |                  |                   |                        |                      |                           |               |             |                        |     |                         |      |       |
| T4JA155K025C□LQ4^00   | A         | 1.5              | 25                | 85                     | 17                   | 125                       | 0.4           | 6           | 3000                   | 3   | 158                     | 142  | 63    |
| T4JB225K025C□LQ4^00   | B         | 2.2              | 25                | 85                     | 17                   | 125                       | 0.6           | 6           | 2000                   | 3   | 206                     | 186  | 82    |
| T4JB335K025C□LQ4^00   | B         | 3.3              | 25                | 85                     | 17                   | 125                       | 0.8           | 6           | 2000                   | 3   | 206                     | 186  | 82    |
| T4JB475K025C□LQ4^00   | B         | 4.7              | 25                | 85                     | 17                   | 125                       | 1.2           | 6           | 2000                   | 3   | 206                     | 186  | 82    |
| T4JC685K025C□LQ4^00   | C         | 6.8              | 25                | 85                     | 17                   | 125                       | 1.7           | 6           | 600                    | 3   | 428                     | 385  | 171   |
| T4JC106K025C□LQ4^00   | C         | 10               | 25                | 85                     | 17                   | 125                       | 2.5           | 6           | 600                    | 3   | 428                     | 385  | 171   |
| T4JC156K025C□LQ4^00   | C         | 15               | 25                | 85                     | 17                   | 125                       | 3.8           | 6           | 600                    | 3   | 428                     | 385  | 171   |
| T4JD226K025C□LQ4^00   | D         | 22               | 25                | 85                     | 17                   | 125                       | 5.5           | 6           | 400                    | 3   | 612                     | 551  | 245   |
| T4JD336K025C□LQ4^00   | D         | 33               | 25                | 85                     | 17                   | 125                       | 8.3           | 6           | 400                    | 3   | 612                     | 551  | 245   |
| T4JD476K025C□LQ4^00   | D         | 47               | 25                | 85                     | 17                   | 125                       | 11.8          | 6           | 400                    | 3   | 612                     | 551  | 245   |
| <b>35 Volt @ 85°C</b> |           |                  |                   |                        |                      |                           |               |             |                        |     |                         |      |       |
| T4JA105K035C□LQ4^00   | A         | 1.0              | 35                | 85                     | 23                   | 125                       | 0.4           | 6           | 3000                   | 3   | 158                     | 142  | 63    |
| T4JA105K035L□LQ4^00   | A         | 1.0              | 35                | 85                     | 23                   | 125                       | 0.2           | 6           | 1000                   | 3   | 274                     | 246  | 110   |
| T4JB155K035C□LQ4^00   | B         | 1.5              | 35                | 85                     | 23                   | 125                       | 0.5           | 6           | 2500                   | 3   | 184                     | 166  | 74    |
| T4JB225K035C□LQ4^00   | B         | 2.2              | 35                | 85                     | 23                   | 125                       | 0.8           | 6           | 2500                   | 3   | 184                     | 166  | 74    |
| T4JB335K035C□LQ4^00   | B         | 3.3              | 35                | 85                     | 23                   | 125                       | 1.2           | 6           | 2500                   | 3   | 184                     | 166  | 74    |
| T4JC475K035C□LQ4^00   | C         | 4.7              | 35                | 85                     | 23                   | 125                       | 1.6           | 6           | 600                    | 3   | 428                     | 385  | 171   |
| T4JC685K035C□LQ4^00   | C         | 6.8              | 35                | 85                     | 23                   | 125                       | 2.4           | 6           | 600                    | 3   | 428                     | 385  | 171   |
| T4JC106K035C□LQ4^00   | C         | 10               | 35                | 85                     | 23                   | 125                       | 3.5           | 6           | 600                    | 3   | 428                     | 385  | 171   |
| T4JD156K035C□LQ4^00   | D         | 15               | 35                | 85                     | 23                   | 125                       | 5.3           | 6           | 400                    | 3   | 612                     | 551  | 245   |
| T4JD226K035C□LQ4^00   | D         | 22               | 35                | 85                     | 23                   | 125                       | 7.7           | 6           | 400                    | 3   | 612                     | 551  | 245   |
| T4JE336K035C□LQ4^00   | E         | 33               | 35                | 85                     | 23                   | 125                       | 11.6          | 6           | 250                    | 3   | 812                     | 731  | 325   |
| T4JV686K035C□LQ4^00   | V         | 68               | 35                | 85                     | 23                   | 125                       | 23.8          | 6           | 500                    | 3   | 707                     | 636  | 283   |
| <b>50 Volt @ 85°C</b> |           |                  |                   |                        |                      |                           |               |             |                        |     |                         |      |       |
| T4JC105K050C□LQ4^00   | C         | 1                | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 1500                   | 3   | 271                     | 244  | 108   |
| T4JC155K050C□LQ4^00   | C         | 1.5              | 50                | 85                     | 33                   | 125                       | 0.8           | 6           | 1500                   | 3   | 271                     | 244  | 108   |
| T4JC225K050C□LQ4^00   | C         | 2.2              | 50                | 85                     | 33                   | 125                       | 1.1           | 6           | 1500                   | 3   | 271                     | 244  | 108   |
| T4JC335K050C□LQ4^00   | C         | 3.3              | 50                | 85                     | 33                   | 125                       | 1.7           | 6           | 1500                   | 3   | 271                     | 244  | 108   |
| T4JD475K050C□LQ4^00   | D         | 4.7              | 50                | 85                     | 33                   | 125                       | 2.4           | 4.5         | 600                    | 3   | 500                     | 450  | 200   |
| T4JD685K050C□LQ4^00   | D         | 6.8              | 50                | 85                     | 33                   | 125                       | 3.4           | 4.5         | 600                    | 3   | 500                     | 450  | 200   |
| T4JE106K050C□LQ4^00   | E         | 10               | 50                | 85                     | 33                   | 125                       | 5.0           | 4.5         | 400                    | 3   | 642                     | 578  | 257   |

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

The EIA & CECC standards for low ESR Solid Tantalum Capacitors allow an ESR movement to 1.25 times catalogue limit post mounting.

# T4J – Medical Series



## HRC4000 Implantable Non Life Support and Non Implantable Life Support

### QUALIFICATION TABLE

| TEST                  | T4J HRC4000 (Temperature range -55°C to +125°C)  |               |                |                    |                              |           |            |            |            |            |  |
|-----------------------|--|---------------|----------------|--------------------|------------------------------|-----------|------------|------------|------------|------------|--|
|                       | Condition  |               |                | Characteristics    |                              |           |            |            |            |            |  |
| Endurance             | Determine after application of rated voltage for 2000 +48/-0 hours at 85±2°C and then leaving 1-2 hours at room temperature. Also determine of 125°C temperature, category voltage for 2000 +48/-0 hours and then leaving 1-2 hours at room temperature. Power supply impedance to be ≤0.1Ω/V. |               |                | Visual examination | no visible damage            |           |            |            |            |            |  |
|                       |  |               |                | DCL                | 1.25 x initial limit         |           |            |            |            |            |  |
|                       |  |               |                | ΔC/C               | within ±10% of initial value |           |            |            |            |            |  |
|                       |  |               |                | DF                 | initial limit                |           |            |            |            |            |  |
|                       |  |               |                | ESR                | 1.25 x initial limit         |           |            |            |            |            |  |
| Storage Life          | 125°C, 0V, 2000h   |               |                | Visual examination | no visible damage            |           |            |            |            |            |  |
|                       |  |               |                | DCL                | 1.25 x initial limit         |           |            |            |            |            |  |
|                       |  |               |                | ΔC/C               | within ±10% of initial value |           |            |            |            |            |  |
|                       |  |               |                | DF                 | initial limit                |           |            |            |            |            |  |
|                       |  |               |                | ESR                | 1.25 x initial limit         |           |            |            |            |            |  |
| Temperature Stability | Step   | Temperature°C | Duration (min) |                    | +20°C                        | -55°C     | +20°C      | +85°C      | +125°C     | +20°C      |  |
|                       | 1  | +20±2         | 15             | DCL                | IL*                          | n/a       | IL*        | 10 x IL*   | 12.5 x IL* | IL*        |  |
|                       | 2  | -55+0/-3      | 15             | ΔC/C               | n/a                          | +0/-10%   | ±5%        | +10/-0%    | +12/-0%    | ±5%        |  |
|                       | 3  | +20±2         | 15             | DF                 | IL*                          | 1.5 x IL* | IL*        | 1.5 x IL*  | 2 x IL*    | IL*        |  |
|                       | 4  | +85+3/-0      | 15             | ESR                | 1.25 x IL*                   | 2.5 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* |  |
|                       | 5  | +125+3/-0     | 15             |                    |                              |           |            |            |            |            |  |
|                       | 6  | +20±2         | 15             |                    |                              |           |            |            |            |            |  |
| Surge Voltage         | Test temperature: 125°C+3/0°C<br>Test voltage: Category voltage at 125°C<br>Surge voltage: 1.3x category voltage at 125°C<br>Series protection resistance 1000±100Ω<br>Discharge resistance: 1000Ω<br>Number of cycles: 1000x<br>Cycle duration: 6min; 30 sec charge,<br>5min 30 sec discharge |               |                | Visual examination | no visible damage            |           |            |            |            |            |  |
|                       |  |               |                | DCL                | initial limit                |           |            |            |            |            |  |
|                       |  |               |                | ΔC/C               | within ±5% of initial value  |           |            |            |            |            |  |
|                       |  |               |                | DF                 | initial limit                |           |            |            |            |            |  |
|                       |  |               |                | ESR                | 1.25 x initial limit         |           |            |            |            |            |  |


\*Initial Limit

### LOT ACCEPTANCE TESTING

| TEST                | T4J HRC4000 (Temperature range -55°C to +125°C)   |                    |                             |
|---------------------|---|--------------------|-----------------------------|
|                     | Condition   | Characteristics    |                             |
| Lot Acceptance Test | 25 Pieces from each lot<br>• Read and Record Initial Electricals<br>• Bake Out @ 125°C for 2 Hours<br>• Mount using AVX recommended profile<br>• Read and Record Post Mounting Electricals<br>• Life Test: 6 hours, 2/3 R.V., 125°C<br>• Read and Record Post Electricals | DCL                | initial limit               |
|                     |   | ΔC/C               | within ±5% of initial value |
|                     |   | DF                 | initial limit               |
|                     |   | ESR                | 1.25 x initial limit        |
|                     |   | 0 Failures Allowed |                             |

# TBM Multianode

## Tantalum Ultra Low ESR Space Level



TBM Space Level series is screened to SRC9000 and utilizes an internal multi-anode design to achieve ultra-low ESR which improves performance in high ripple power application.


TBM Space Level is available with Weibull Grade "C" reliability and MIL-PRF-55365 Rev. G surge test option "C".

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these correspond to

"H", "K", "C" and "B" termination, respectively, per MIL-PRF-55365).

The molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.




### CASE DIMENSIONS: millimeters (inches)

| Code | L±0.20<br>(0.008) | W+0.20 (0.008)<br>-0.10 (0.004) | H+0.20 (0.008)<br>-0.10 (0.004) | W <sub>1</sub> ±0.20<br>(0.008) | A+0.30 (0.012)<br>-0.20 (0.008) | S Min.       |
|------|-------------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------|--------------|
| D    | 7.30 (0.287)      | 4.30 (0.169)                    | 2.90 (0.114)                    | 2.40 (0.094)                    | 1.30 (0.051)                    | 4.40 (0.173) |
| E    | 7.30 (0.287)      | 4.30 (0.169)                    | 4.10 (0.162)                    | 2.40 (0.094)                    | 1.30 (0.051)                    | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### MARKING

#### D, E CASE




### CAPACITANCE AND RATED VOLTAGE RANGE LETTER DENOTES CASE SIZE ESR LIMIT IN BRACKETS

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) to 85°C |        |        |         |         |          |          |         |                    |
|-------------|------|--|--------|--------|---------|---------|----------|----------|---------|--------------------|
| µF          | Code | 2.5V (e)                                   | 4V (G) | 6V (J) | 10V (A) | 12V (B) | 16V (C)  | 20V (D)  | 25V (E) | 35V (V)            |
| 22          | 226  |  |        |        |         |         |          |          |         | D(70)<br>E(60,100) |
| 33          | 336  |  |        |        |         |         |          |          | D(65)   | E(50,65)           |
| 47          | 476  |  |        |        |         |         |          |          | E(65)   |                    |
| 68          | 686  |  |        |        |         |         |          |          |         |                    |
| 100         | 107  |  |        |        |         |         |          | E(35,45) |         |                    |
| 150         | 157  |  |        |        |         |         | E(30,40) |          |         |                    |
| 220         | 227  |  |        |        | D(35)   | E(35)   |          |          |         |                    |
| 330         | 337  |  | D(35)  | D(35)  | E(35)   |         |          |          |         |                    |
| 470         | 477  |  | D(35)  | E(30)  |         |         |          |          |         |                    |
| 680         | 687  |  | E(23)  |        |         |         |          |          |         |                    |
| 1000        | 108  | D(25)                                      | E(23)  |        |         |         |          |          |         |                    |
| 1500        | 158  | E(18)                                      |        |        |         |         |          |          |         |                    |


Available Ratings: ESR limits quoted in brackets (mOhms)

Notes: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards. EIA standards for Low ESR solid tantalum capacitors allow an ESR movement of 1.25 times initial limit post mounting.

#### MULTIANODE CONSTRUCTION



#### MULTIANODE TBM D LOW SELF INDUCTANCE CONSTRUCTION "MIRROR" DESIGN





# TBM Multianode



## Tantalum Ultra Low ESR Space Level

### HOW TO ORDER

#### SPACE LEVEL OPTIONS TO SRC9000:

| TBM  | E                | 477   | *                            | 006  | L                                | □   | L                       | @  | 9                          | ^  | ++   |
|--|------------------|---|------------------------------|--|----------------------------------|---|-------------------------|--|----------------------------|--|--|
| <b>Type</b>  | <b>Case Size</b> | <b>Capacitance Code</b>   | <b>Capacitance Tolerance</b> | <b>Voltage Code</b>  | <b>Standard or Low ESR Range</b> | <b>Packaging</b>  | <b>Inspection Level</b> | <b>Reliability Grade</b>                     | <b>Qualification Level</b> | <b>Termination Finish</b>  | <b>Surge Test Option</b>                     |
|  |                  | pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | M = ±20%<br>K = ±10%         | 002 = 2.5Vdc<br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>012 = 12Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc | C = Std ESR<br>L = Low ESR       | B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | L = Group A             | Weibull:<br>C = 0.01%/1000 hrs.<br>90% conf. | 9 = SRC9000                | H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated | 45 = 10 cycles, -55°C & +85°C before Weibull |
|   <p>For RoHS compliant products, please select correct termination style.</p> |                  |   |                              |  |                                  |   |                         |  |                            |  |  |

### TECHNICAL SPECIFICATIONS

Technical Data: Unless otherwise specified, all technical data relate to an ambient temperature of +25°C

|                            |                  |     |     |   |    |      |    |    |    |    |  |
|----------------------------|------------------|-----|-----|---|----|------|----|----|----|----|--|
| Capacitance Range:         | 22 µF to 1500 µF |     |     |   |    |      |    |    |    |    |  |
| Capacitance Tolerance:     | ±10%; ±20%       |     |     |   |    |      |    |    |    |    |  |
| Rated Voltage DC ( $V_R$ ) | ≤ +85°C:         | 2.5 | 4   | 6 | 10 | 12   | 16 | 20 | 25 | 35 |  |
| Category Voltage ( $V_C$ ) | ≤ +125°C:        | 1.7 | 2.7 | 4 | 7  | 8.4  | 10 | 13 | 17 | 23 |  |
| Surge Voltage ( $V_S$ )    | ≤ +85°C:         | 3.3 | 5.2 | 8 | 13 | 15.6 | 20 | 26 | 32 | 46 |  |
| Surge Voltage ( $V_S$ )    | ≤ +125°C:        | 2.2 | 3.4 | 5 | 8  | 9.6  | 12 | 16 | 20 | 28 |  |
| Temperature Range:         | -55°C to +125°C  |     |     |   |    |      |    |    |    |    |  |

# TBM Multianode



## Tantalum Ultra Low ESR Space Level


| RATING & PART NUMBER REFERENCE            |      | Parametric Specifications by Rating |                               |                               |               |               |                |              |                  |              | Typical RMS Ripple Data by Rating |                           |                           |                            |                           |                           |                            |
|---|------|-------------------------------------|-------------------------------|-------------------------------|---------------|---------------|----------------|--------------|------------------|--------------|-----------------------------------|---------------------------|---------------------------|----------------------------|---------------------------|---------------------------|----------------------------|
|   |      | Cap @ 120Hz<br>µF @ 25°C            | DC Rated Voltage<br>V @ +85°C | ESR @ 100kHz<br>mOhms @ +25°C | DCL max       |               |                | DF max       |                  |              | Power Dissipation<br>W            | 25°C Ripple<br>A (100kHz) | 85°C Ripple<br>A (100kHz) | 125°C Ripple<br>A (100kHz) | 25°C Ripple<br>V (100kHz) | 85°C Ripple<br>V (100kHz) | 125°C Ripple<br>V (100kHz) |
|   |      |                                     |                               |                               | +25°C<br>(µA) | +85°C<br>(µA) | +125°C<br>(µA) | +25°C<br>(%) | +85/125°C<br>(%) | -55°C<br>(%) |                                   |                           |                           |                            |                           |                           |                            |
| AVX P/N                                   | Case |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| <b>2.5 Volt @ 85°C (1.7 Volt @ 125°C)</b> |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBMD108*002L□LC9^45                       | D    | 1000                                | 2.5                           | 25                            | 18.8          | 188           | 376            | 8            | 11               | 12           | 0.255                             | 3.194                     | 2.874                     | 1.277                      | 0.080                     | 0.072                     | 0.032                      |
| TBME158*002C□LC9^45                       | E    | 1500                                | 2.5                           | 18                            | 28.1          | 281           | 562            | 6            | 9                | 10           | 0.270                             | 3.873                     | 3.486                     | 1.549                      | 0.070                     | 0.063                     | 0.028                      |
| <b>4 Volt @ 85°C (2.7 Volt @ 125°C)</b>   |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBMD337*004L□LC9^45                       | D    | 330                                 | 4                             | 35                            | 9.9           | 99            | 198            | 8            | 11               | 12           | 0.255                             | 2.699                     | 2.429                     | 1.080                      | 0.094                     | 0.085                     | 0.038                      |
| TBMD477*004L□LC9^45                       | D    | 470                                 | 4                             | 35                            | 14.1          | 141           | 282            | 8            | 11               | 12           | 0.255                             | 2.699                     | 2.429                     | 1.080                      | 0.094                     | 0.085                     | 0.038                      |
| TBME687*004C□LC9^45                       | E    | 680                                 | 4                             | 23                            | 20.4          | 204           | 408            | 6            | 9                | 10           | 0.270                             | 3.426                     | 3.084                     | 1.370                      | 0.079                     | 0.071                     | 0.032                      |
| TBME108*004C□LC9^45                       | E    | 1000                                | 4                             | 23                            | 30            | 300           | 600            | 6            | 9                | 10           | 0.270                             | 3.426                     | 3.084                     | 1.370                      | 0.079                     | 0.071                     | 0.032                      |
| <b>6 Volt @ 85°C (4 Volt @ 125°C)</b>     |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBMD337*006L□LC9^45                       | D    | 330                                 | 6                             | 35                            | 14.9          | 149           | 298            | 8            | 11               | 12           | 0.255                             | 2.699                     | 2.429                     | 1.080                      | 0.094                     | 0.085                     | 0.038                      |
| TBME477*006C□LC9^45                       | E    | 470                                 | 6                             | 30                            | 21.2          | 212           | 424            | 6            | 9                | 10           | 0.270                             | 3.000                     | 2.700                     | 1.200                      | 0.090                     | 0.081                     | 0.036                      |
| <b>10 Volt @ 85°C (7 Volt @ 125°C)</b>    |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBMD227*010L□LC9^45                       | D    | 220                                 | 10                            | 35                            | 16.5          | 165           | 330            | 8            | 11               | 12           | 0.255                             | 2.699                     | 2.429                     | 1.080                      | 0.094                     | 0.085                     | 0.038                      |
| TBME337*010C□LC9^45                       | E    | 330                                 | 10                            | 35                            | 24.8          | 248           | 496            | 6            | 9                | 10           | 0.270                             | 2.777                     | 2.500                     | 1.111                      | 0.097                     | 0.087                     | 0.039                      |
| <b>12 Volt @ 85°C (8.4 Volt @ 125°C)</b>  |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBME227*012C□LC9^45                       | E    | 220                                 | 12                            | 35                            | 19.8          | 198           | 396            | 6            | 9                | 10           | 0.270                             | 2.777                     | 2.500                     | 1.111                      | 0.097                     | 0.087                     | 0.039                      |
| <b>16 Volt @ 85°C (10 Volt @ 125°C)</b>   |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBME157*016L□LC9^45                       | E    | 150                                 | 16                            | 30                            | 18            | 180           | 360            | 6            | 9                | 10           | 0.270                             | 3.000                     | 2.700                     | 1.200                      | 0.090                     | 0.081                     | 0.036                      |
| TBME157*016C□LC9^45                       | E    | 150                                 | 16                            | 40                            | 18            | 180           | 360            | 6            | 9                | 10           | 0.270                             | 2.598                     | 2.338                     | 1.039                      | 0.104                     | 0.094                     | 0.042                      |
| <b>20 Volt @ 85°C (13 Volt @ 125°C)</b>   |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBME107*020L□LC9^45                       | E    | 100                                 | 20                            | 35                            | 15            | 150           | 300            | 6            | 9                | 10           | 0.270                             | 2.777                     | 2.500                     | 1.111                      | 0.097                     | 0.087                     | 0.039                      |
| TBME107*020C□LC9^45                       | E    | 100                                 | 20                            | 45                            | 15            | 150           | 300            | 6            | 9                | 10           | 0.270                             | 2.449                     | 2.205                     | 0.980                      | 0.110                     | 0.099                     | 0.044                      |
| <b>25 Volt @ 85°C (17 Volt @ 125°C)</b>   |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBMD336*025L□LC9^45                       | D    | 33                                  | 25                            | 65                            | 6.2           | 62            | 124            | 8            | 11               | 12           | 0.255                             | 1.981                     | 1.783                     | 0.792                      | 0.129                     | 0.116                     | 0.051                      |
| TBME476*025L□LC9^45                       | E    | 47                                  | 25                            | 65                            | 8.8           | 88            | 176            | 6            | 9                | 10           | 0.270                             | 2.038                     | 1.834                     | 0.815                      | 0.132                     | 0.119                     | 0.053                      |
| <b>35 Volt @ 85°C (23 Volt @ 125°C)</b>   |      |                                     |                               |                               |               |               |                |              |                  |              |                                   |                           |                           |                            |                           |                           |                            |
| TBMD226*035L□LC9^45                       | D    | 22                                  | 35                            | 70                            | 5.8           | 58            | 116            | 8            | 11               | 12           | 0.255                             | 1.909                     | 1.718                     | 0.763                      | 0.134                     | 0.120                     | 0.053                      |
| TBME226*035L□LC9^45                       | E    | 22                                  | 35                            | 60                            | 5.8           | 58            | 116            | 6            | 9                | 10           | 0.270                             | 2.121                     | 1.909                     | 0.849                      | 0.127                     | 0.115                     | 0.051                      |
| TBME226*035C□LC9^45                       | E    | 22                                  | 35                            | 100                           | 5.8           | 58            | 116            | 6            | 9                | 10           | 0.270                             | 1.643                     | 1.479                     | 0.657                      | 0.164                     | 0.148                     | 0.066                      |
| TBME336*035L□LC9^45                       | E    | 33                                  | 35                            | 50                            | 8.7           | 87            | 174            | 6            | 9                | 10           | 0.270                             | 2.324                     | 2.091                     | 0.930                      | 0.116                     | 0.105                     | 0.046                      |
| TBME336*035C□LC9^45                       | E    | 33                                  | 35                            | 65                            | 8.7           | 87            | 174            | 6            | 9                | 10           | 0.270                             | 2.038                     | 1.834                     | 0.815                      | 0.132                     | 0.119                     | 0.053                      |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

# TBM Multianode

## Tantalum Ultra Low ESR COTS-Plus



TBM COTS-Plus series uses an internal multi-anode design to achieve ultra-low ESR which improves performance in high ripple power applications.


TBM is available with Weibull Grade “B” reliability and all MIL-PRF-55365 Rev. G surge test options (“A”, “B” & “C”).

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these

correspond to “H”, “K”, “C” and “B” termination, respectively, per MIL-PRF-55365).

The molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of ASTM E-595.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.




### CASE DIMENSIONS: millimeters (inches)

| Code | L±0.20<br>(0.008) | W+0.20 (0.008)<br>-0.10 (0.004) | H+0.20 (0.008)<br>-0.10 (0.004) | W <sub>1</sub> ±0.20<br>(0.008) | A+0.30 (0.012)<br>-0.20 (0.008) | S Min.       |
|------|-------------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------|--------------|
| D    | 7.30 (0.287)      | 4.30 (0.169)                    | 2.90 (0.114)                    | 2.40 (0.094)                    | 1.30 (0.051)                    | 4.40 (0.173) |
| E    | 7.30 (0.287)      | 4.30 (0.169)                    | 4.10 (0.162)                    | 2.40 (0.094)                    | 1.30 (0.051)                    | 4.40 (0.173) |
| V    | 7.30 (0.287)      | 6.10 (0.240)                    | 3.55 (0.140)                    | 3.10 (0.120)                    | 1.30 (0.051)                    | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### MARKING

#### D, E, V CASE




### CAPACITANCE AND RATED VOLTAGE RANGE LETTER DENOTES CASE SIZE ESR LIMIT IN BRACKETS

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) to 85°C |                   |              |          |         |          |          |         |                    |
|-------------|------|--|-------------------|--------------|----------|---------|----------|----------|---------|--------------------|
| µF          | Code | 2.5V (e)                                   | 4V (G)            | 6V (J)       | 10V (A)  | 12V (B) | 16V (C)  | 20V (D)  | 25V (E) | 35V (V)            |
| 22          | 226  |  |                   |              |          |         |          |          |         | D(70)<br>E(60,100) |
| 33          | 336  |  |                   |              |          |         |          |          | D(65)   | E(50,65)           |
| 47          | 476  |  |                   |              |          |         |          |          | E(65)   | E(55)              |
| 68          | 686  |  |                   |              |          |         |          |          | E(45)   |                    |
| 100         | 107  |  |                   |              |          |         |          | E(35,45) |         |                    |
| 150         | 157  |  |                   |              |          |         | E(30,40) |          |         |                    |
| 220         | 227  |  |                   |              | D(35)    | E(35)   | E(25)    |          |         |                    |
| 330         | 337  |  | D(35)             | D(35)        | E(23,35) |         |          |          |         |                    |
| 470         | 477  |  | D(35)             | E(18,30)     | E(23)    |         |          |          |         |                    |
| 680         | 687  |  | E(18,23)          | E(18), V(23) |          |         |          |          |         |                    |
| 1000        | 108  | D(25)                                      | E(18,23)<br>V(18) |              |          |         |          |          |         |                    |
| 1500        | 158  | E(12,18)                                   | E(15)             |              |          |         |          |          |         |                    |
| 2000        | 208  |  |                   |              |          |         |          |          |         |                    |


Available Ratings: ESR limits quoted in brackets (mOhms)

Notes: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards. EIA standards for Low ESR solid tantalum capacitors allow an ESR movement of 1.25 times initial limit post mounting.

#### MULTIANODE CONSTRUCTION



#### MULTIANODE TBM D LOW SELF INDUCTANCE CONSTRUCTION "MIRROR" DESIGN



# TBM Multianode



## Tantalum Ultra Low ESR COTS-Plus

### HOW TO ORDER

#### COTS-PLUS:

| TBM  | E         | 477  | *   | 006  | L   | □  | #   | @   | 0                              | ^  | ++   |
|------|-----------|--|---|--|---|--|---|---|--------------------------------|--|--|
| Type | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>M = ±20%<br>K = ±10% | Voltage Code<br>002 = 2.5Vdc<br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>012 = 12Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc | Standard or Low ESR Range<br>C = Std ESR<br>L = Low ESR | Packaging<br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | Inspection Level<br>S = Std. Conformance<br>L = Group A | Reliability Grade<br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>Z = Non-ER | Qualification Level<br>0 = N/A | Termination Finish<br>H = Solder Plated<br>0 = Fused Solder Plated<br>8 = Hot Solder Dipped<br>9 = Gold Plated<br>7 = Matte Sn | Surge Test Option<br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |



### TECHNICAL SPECIFICATIONS

Technical Data: Unless otherwise specified, all technical data relate to an ambient temperature of +25°C

|                                    |                  |     |     |   |    |      |    |    |    |    |  |
|------------------------------------|------------------|-----|-----|---|----|------|----|----|----|----|--|
| Capacitance Range:                 | 22 µF to 1500 µF |     |     |   |    |      |    |    |    |    |  |
| Capacitance Tolerance:             | ±10%; ±20%       |     |     |   |    |      |    |    |    |    |  |
| Rated Voltage DC (V <sub>R</sub> ) | ≤ +85°C:         | 2.5 | 4   | 6 | 10 | 12   | 16 | 20 | 25 | 35 |  |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C:        | 1.7 | 2.7 | 4 | 7  | 8.4  | 10 | 13 | 17 | 23 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +85°C:         | 3.3 | 5.2 | 8 | 13 | 15.6 | 20 | 26 | 32 | 46 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +125°C:        | 2.2 | 3.4 | 5 | 8  | 9.6  | 12 | 16 | 20 | 28 |  |
| Temperature Range:                 | -55°C to +125°C  |     |     |   |    |      |    |    |    |    |  |



# TBM Multianode

## Tantalum Ultra Low ESR COTS-Plus



| RATING & PART NUMBER REFERENCE            |      | Parametric Specifications by Rating |                  |               |         |       |        |        |           |       | Typical RMS Ripple Data by Rating |                     |                     |                      |                     |                     |                      |
|---|------|-------------------------------------|------------------|---------------|---------|-------|--------|--------|-----------|-------|-----------------------------------|---------------------|---------------------|----------------------|---------------------|---------------------|----------------------|
|   |      | Cap @ 120Hz                         | DC Rated Voltage | ESR @ 100kHz  | DCL max |       |        | DF max |           |       | Power Dissipation                 | 25°C Ripple Current | 85°C Ripple Current | 125°C Ripple Current | 25°C Ripple Voltage | 85°C Ripple Voltage | 125°C Ripple Voltage |
|   |      |                                     |                  |               | +25°C   | +85°C | +125°C | +25°C  | +85/125°C | -55°C |                                   |                     |                     |                      |                     |                     |                      |
| AVX P/N                                   | Case | µF @ 25°C                           | V @ +85°C        | mOhms @ +25°C | (µA)    | (µA)  | (µA)   | (%)    | (%)       | (%)   | W                                 | A (100kHz)          | A (100kHz)          | A (100kHz)           | V (100kHz)          | V (100kHz)          | V (100kHz)           |
| <b>2.5 Volt @ 85°C (1.7 Volt @ 125°C)</b> |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBMD108*002L□SB0^++                       | D    | 1000                                | 2.5              | 25            | 18.8    | 188   | 376    | 8      | 11        | 12    | 0.255                             | 3.194               | 2.874               | 1.277                | 0.080               | 0.072               | 0.032                |
| TBME158*002C□SB0^++                       | E    | 1500                                | 2.5              | 18            | 28.1    | 281   | 562    | 6      | 9         | 10    | 0.270                             | 3.873               | 3.486               | 1.549                | 0.070               | 0.063               | 0.028                |
| TBME158*002L□SB0^++                       | E    | 1500                                | 2.5              | 12            | 38      | 380   | 760    | 6      | 9         | 10    | 0.270                             | 4.743               | 4.269               | 1.897                | 0.057               | 0.051               | 0.023                |
| <b>4 Volt @ 85°C (2.7 Volt @ 125°C)</b>   |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBMD337*004L□SB0^++                       | D    | 330                                 | 4                | 35            | 9.9     | 99    | 198    | 8      | 11        | 12    | 0.255                             | 2.699               | 2.429               | 1.080                | 0.094               | 0.085               | 0.038                |
| TBMD477*004L□SB0^++                       | D    | 470                                 | 4                | 35            | 14.1    | 141   | 282    | 8      | 11        | 12    | 0.255                             | 2.699               | 2.429               | 1.080                | 0.094               | 0.085               | 0.038                |
| TBME687*004C□SB0^++                       | E    | 680                                 | 4                | 23            | 20.4    | 204   | 408    | 6      | 9         | 10    | 0.270                             | 3.426               | 3.084               | 1.370                | 0.079               | 0.071               | 0.032                |
| TBME687*004L□SB0^++                       | E    | 680                                 | 4                | 18            | 27      | 270   | 540    | 6      | 9         | 10    | 0.270                             | 3.873               | 3.486               | 1.549                | 0.070               | 0.063               | 0.028                |
| TBME108*004C□SB0^++                       | E    | 1000                                | 4                | 23            | 30      | 300   | 600    | 6      | 9         | 10    | 0.270                             | 3.426               | 3.084               | 1.370                | 0.079               | 0.071               | 0.032                |
| TBME108*004L□SB0^++                       | E    | 1000                                | 4                | 18            | 40      | 400   | 800    | 6      | 9         | 10    | 0.270                             | 3.873               | 3.486               | 1.549                | 0.070               | 0.063               | 0.028                |
| TBMV108*004L□SB0^++                       | V    | 1000                                | 4                | 18            | 40      | 400   | 800    | 6      | 9         | 10    | 0.285                             | 3.979               | 3.581               | 1.592                | 0.072               | 0.064               | 0.029                |
| TBME158*004L□SB0^++                       | E    | 1500                                | 4                | 15            | 40      | 400   | 800    | 6      | 9         | 10    | 0.270                             | 4.243               | 3.818               | 1.697                | 0.064               | 0.057               | 0.025                |
| <b>6 Volt @ 85°C (4 Volt @ 125°C)</b>     |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBMD337*006L□SB0^++                       | D    | 330                                 | 6                | 35            | 14.9    | 149   | 298    | 8      | 11        | 12    | 0.255                             | 2.699               | 2.429               | 1.080                | 0.094               | 0.085               | 0.038                |
| TBME477*006C□SB0^++                       | E    | 470                                 | 6                | 30            | 21.2    | 212   | 424    | 6      | 9         | 10    | 0.270                             | 3.000               | 2.700               | 1.200                | 0.090               | 0.081               | 0.036                |
| TBME477*006L□SB0^++                       | E    | 470                                 | 6                | 18            | 28      | 280   | 560    | 6      | 9         | 10    | 0.270                             | 3.873               | 3.486               | 1.549                | 0.070               | 0.063               | 0.028                |
| TBME687*006L□SB0^++                       | E    | 680                                 | 6                | 18            | 41      | 410   | 820    | 6      | 9         | 10    | 0.270                             | 3.873               | 3.486               | 1.549                | 0.070               | 0.063               | 0.028                |
| TBMV687*006L□SB0^++                       | V    | 680                                 | 6                | 23            | 41      | 410   | 820    | 6      | 9         | 10    | 0.285                             | 3.520               | 3.168               | 1.408                | 0.081               | 0.073               | 0.032                |
| <b>10 Volt @ 85°C (7 Volt @ 125°C)</b>    |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBMD227*010L□SB0^++                       | D    | 220                                 | 10               | 35            | 16.5    | 165   | 330    | 8      | 11        | 12    | 0.255                             | 2.699               | 2.429               | 1.080                | 0.094               | 0.085               | 0.038                |
| TBME337*010C□SB0^++                       | E    | 330                                 | 10               | 35            | 24.8    | 248   | 496    | 6      | 9         | 10    | 0.270                             | 2.777               | 2.500               | 1.111                | 0.097               | 0.087               | 0.039                |
| TBME337*010L□SB0^++                       | E    | 330                                 | 10               | 23            | 33      | 330   | 660    | 6      | 9         | 10    | 0.270                             | 3.426               | 3.084               | 1.370                | 0.079               | 0.071               | 0.032                |
| TBME477*010L□SB0^++                       | E    | 470                                 | 10               | 23            | 47      | 470   | 940    | 6      | 9         | 10    | 0.270                             | 3.426               | 3.084               | 1.370                | 0.079               | 0.071               | 0.032                |
| <b>12 Volt @ 85°C (8.4 Volt @ 125°C)</b>  |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBME227*012C□SB0^++                       | E    | 220                                 | 12               | 35            | 19.8    | 198   | 396    | 6      | 9         | 10    | 0.270                             | 2.777               | 2.500               | 1.111                | 0.097               | 0.087               | 0.039                |
| <b>16 Volt @ 85°C (10 Volt @ 125°C)</b>   |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBME157*016C□SB0^++                       | E    | 150                                 | 16               | 40            | 18      | 180   | 360    | 6      | 9         | 10    | 0.270                             | 2.598               | 2.338               | 1.039                | 0.104               | 0.094               | 0.042                |
| TBME157*016L□SB0^++                       | E    | 150                                 | 16               | 30            | 18      | 180   | 360    | 6      | 9         | 10    | 0.270                             | 3.000               | 2.700               | 1.200                | 0.090               | 0.081               | 0.036                |
| TBME227*016L□SB0^++                       | E    | 220                                 | 16               | 25            | 35      | 350   | 700    | 6      | 9         | 10    | 0.270                             | 3.286               | 2.958               | 1.315                | 0.082               | 0.074               | 0.033                |
| <b>20 Volt @ 85°C (13 Volt @ 125°C)</b>   |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBME107*020C□SB0^++                       | E    | 100                                 | 20               | 45            | 15      | 150   | 300    | 6      | 9         | 10    | 0.270                             | 2.449               | 2.205               | 0.980                | 0.110               | 0.099               | 0.044                |
| TBME107*020L□SB0^++                       | E    | 100                                 | 20               | 35            | 15      | 150   | 300    | 6      | 9         | 10    | 0.270                             | 2.777               | 2.500               | 1.111                | 0.097               | 0.087               | 0.039                |
| <b>25 Volt @ 85°C (17 Volt @ 125°C)</b>   |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBMD336*025L□SB0^++                       | D    | 33                                  | 25               | 65            | 6.2     | 62    | 124    | 8      | 11        | 12    | 0.255                             | 1.981               | 1.783               | 0.792                | 0.129               | 0.116               | 0.051                |
| TBME476*025L□SB0^++                       | E    | 47                                  | 25               | 65            | 8.8     | 88    | 176    | 6      | 9         | 10    | 0.270                             | 2.038               | 1.834               | 0.815                | 0.132               | 0.119               | 0.053                |
| TBME686*025L□SB0^++                       | E    | 68                                  | 25               | 45            | 17      | 170   | 340    | 6      | 9         | 10    | 0.270                             | 2.449               | 2.205               | 0.980                | 0.110               | 0.099               | 0.044                |
| <b>35 Volt @ 85°C (23 Volt @ 125°C)</b>   |      |                                     |                  |               |         |       |        |        |           |       |                                   |                     |                     |                      |                     |                     |                      |
| TBMD226*035L□SB0^++                       | D    | 22                                  | 35               | 70            | 5.8     | 58    | 116    | 8      | 11        | 12    | 0.255                             | 1.909               | 1.718               | 0.763                | 0.134               | 0.120               | 0.053                |
| TBME226*035C□SB0^++                       | E    | 22                                  | 35               | 100           | 5.8     | 58    | 116    | 6      | 9         | 10    | 0.270                             | 1.643               | 1.479               | 0.657                | 0.164               | 0.148               | 0.066                |
| TBME226*035L□SB0^++                       | E    | 22                                  | 35               | 60            | 5.8     | 58    | 116    | 6      | 9         | 10    | 0.270                             | 2.121               | 1.909               | 0.849                | 0.127               | 0.115               | 0.051                |
| TBME336*035C□SB0^++                       | E    | 33                                  | 35               | 65            | 8.7     | 87    | 174    | 6      | 9         | 10    | 0.270                             | 2.038               | 1.834               | 0.815                | 0.132               | 0.119               | 0.053                |
| TBME336*035L□SB0^++                       | E    | 33                                  | 35               | 50            | 8.7     | 87    | 174    | 6      | 9         | 10    | 0.270                             | 2.324               | 2.091               | 0.930                | 0.116               | 0.105               | 0.046                |
| TBME476*035L□SB0^++                       | E    | 47                                  | 35               | 55            | 16      | 160   | 320    | 6      | 9         | 10    | 0.270                             | 2.216               | 1.994               | 0.886                | 0.122               | 0.110               | 0.049                |


All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

# TBC Series



## CWR15 MIL-PRF-55365/12 Established Reliability, COTS-Plus & Space Level




AVX announces the world's smallest military approved tantalum chip capacitors. The CWR15 offers 0603, 0805 and 1206 case sizes in capacitance/voltage combinations previously only available in much larger packages. The revolutionary AVX TACmicrochip® technology offers designers significant opportunity to downsize circuits for military and aerospace applications.

The product is manufactured in the AVX Tantalum high reliability facility in Biddeford, Maine which is also home to the CWR09, CWR11, CWR19 and CWR29 product lines.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.


### CASE DIMENSIONS: millimeters (inches)

| Case Code | Length (L)                              | Width (W)                               | Height (H)                              | Term. Width (W <sub>t</sub> )           |
|-----------|---|---|---|---|
| A         | 3.20±0.20<br>(0.126±0.008)              | 1.60±0.20<br>(0.063±0.008)              | 1.60±0.20<br>(0.063±0.008)              | 0.15+0.35/-0.00<br>(0.006+0.014/-0.000) |
| L         | 1.60+0.25/-0.15<br>(0.063+0.010/-0.006) | 0.84+0.20/-0.10<br>(0.033+0.008/-0.004) | 0.84+0.20/-0.10<br>(0.033+0.008/-0.004) | 0.15+0.35/-0.00<br>(0.006+0.014/-0.000) |
| R         | 2.00+0.25/-0.15<br>(0.079+0.010/-0.006) | 1.35+0.20/-0.10<br>(0.053+0.008/-0.004) | 1.35+0.20/-0.10<br>(0.053+0.008/-0.004) | 0.15+0.35/-0.00<br>(0.006+0.014/-0.000) |



### MARKING

#### A, L, R CASE



### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Voltage Rating DC (V <sub>R</sub> ) at 85°C |        |         |         |
|-------------|------|---|--------|---------|---------|
| µF          | Code | 4V (C)                                      | 6V (D) | 10V (F) | 20V (J) |
| 0.47        | 474  |   |        | L       | L       |
| 0.68        | 684  |   |        | L       |         |
| 1.0         | 105  |   |        | L       |         |
| 1.5         | 155  |   |        | L       |         |
| 2.2         | 225  |   |        | L       |         |
| 3.3         | 335  |   | L      | R       |         |
| 4.7         | 475  |   | L      | R       |         |
| 6.8         | 685  | L   | R      | R       |         |
| 10          | 106  | R   | R      | R       |         |
| 15          | 156  | R   | R      | A       |         |
| 22          | 226  | R   | A      |         |         |
| 33          | 336  | R   | A      |         |         |
| 47          | 476  |   | A      |         |         |
| 68          | 686  | A   |        |         |         |

Further extensions of the CWR15 product are planned for later in 2009. A new case size will be added, and the voltage range will be extended to 20 volts. Ratings of 100 µF at 4 volts to 10 µF at 20 volts will be included in this extension of the product line.

# TBC Series



## CWR15 MIL-PRF-55365/12 Established Reliability, COTS-Plus & Space Level

### HOW TO ORDER

#### COTS-PLUS & MIL QPL (CWR15):

|             |                  |   |   |   |   |   |   |   |   |  |   |
|-------------|------------------|---|---|---|---|---|---|---|---|--|---|
| <b>TBC</b>  | <b>L</b>         | <b>685</b>  | <b>*</b>  | <b>004</b>  | <b>C</b>  | <b>□</b>  | <b>#</b>  | <b>@</b>  | <b>0</b>  | <b>^</b>   | <b>++</b>   |
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>020 = 20Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>S = Std. Conformance<br>L = Group A<br><br>M = MIL (JAN) CWR15 | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>Z = Non-ER | <b>Qualification Level</b><br>0 = N/A<br>T = T Level<br>9 = SRC9000 | <b>Termination Finish</b><br>0 = Fused Solder Plated<br>9 = Gold Plated<br>7 = Matte Sn (COTS-Plus only) | <b>Surge Test Option</b><br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

#### CWR15 P/N CROSS REFERENCE:

|              |   |  |  |   |   |                  |   |
|--------------|---|--|--|---|---|------------------|---|
| <b>CWR15</b> | <b>F</b>  | <b>C</b>   | <b>685</b>   | <b>*</b>  | <b>-</b>  | <b>L</b>         | <b>+</b>  |
| <b>Style</b> | <b>Voltage Code</b><br>C = 4Vdc<br>D = 6Vdc<br>F = 10Vdc<br>J = 20Vdc | <b>Termination Finish</b><br>B = Gold Plated<br>K = Solder Fused | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents number of zeros to follow | <b>Capacitance Tolerance</b><br>J = ±5%<br>K = ±10%<br>M = ±20%<br><br>See page 8 for additional packaging options. | <b>Product Level Designator</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>T = T Level<br>A = Non-ER | <b>Case Size</b> | <b>Surge Test Option</b><br>A = +25°C after Weibull<br>B = -55°C & +85°C after Weibull<br>C = -55°C & +85°C before Weibull<br>Z = None Required |

For RoHS compliant products, please select correct termination style.

#### SPACE LEVEL OPTIONS TO SRC9000\*:

|             |                  |   |   |   |  |   |  |   |   |   |  |
|-------------|------------------|---|---|---|--|---|--|---|---|---|--|
| <b>TBC</b>  | <b>L</b>         | <b>685</b>  | <b>*</b>  | <b>004</b>  | <b>C</b>   | <b>□</b>  | <b>L</b>                               | <b>@</b>  | <b>9</b>                                  | <b>^</b>  | <b>++</b>  |
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>020 = 20Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>L = Group A | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf. | <b>Qualification Level</b><br>9 = SRC9000 | <b>Termination Finish</b><br>0 = Fused Solder Plated<br>9 = Gold Plated | <b>Surge Test Option</b><br>45 = 10 cycles, -55°C & +85°C before Weibull |

For RoHS compliant products, please select correct termination style.

\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |   |     |     |      |      |
|------------------------------------|---|-----|-----|------|------|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of 25°C |     |     |      |      |
| Capacitance Range:                 | 0.47 µF to 68 µF  |     |     |      |      |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%   |     |     |      |      |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 4   | 6   | 10   | 20   |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | 2.7 | 4   | 6.7  | 13.3 |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 5.3 | 8   | 13.3 | 26.7 |
| Surge Voltage (V <sub>S</sub> )    | ≤ 125°C:  | 3.5 | 5.3 | 8.7  | 17.8 |
| Temperature Range:                 | -55°C to +125°C   |     |     |      |      |



# TBC Series



## CWR15 MIL-PRF-55365/12 Established Reliability, COTS-Plus & Space Level

| RATING & PART NUMBER REFERENCE |                                |                                |      | Parametric Specifications by Rating per MIL-PRF-55365/12 |                                     |                                    |         |       |        |        | Typical RMS Ripple Data by Rating |        |                           |                                 |                                 |                                  |                                 |                                 |                                  |
|--------------------------------|--------------------------------|--------------------------------|------|--|-------------------------------------|------------------------------------|---------|-------|--------|--------|-----------------------------------|--------|---------------------------|---------------------------------|---------------------------------|----------------------------------|---------------------------------|---------------------------------|----------------------------------|
|                                |                                |                                |      | Cap<br>@ 120Hz<br>μF<br>@ 25°C                           | DC Rated<br>Voltage<br>V<br>@ +85°C | ESR<br>@ 100kHz<br>Ohms<br>@ +25°C | DCL max |       |        | DF Max |                                   |        | Power<br>Dissipation<br>W | 25°C<br>Ripple<br>A<br>(100kHz) | 85°C<br>Ripple<br>A<br>(100kHz) | 125°C<br>Ripple<br>A<br>(100kHz) | 25°C<br>Ripple<br>V<br>(100kHz) | 85°C<br>Ripple<br>V<br>(100kHz) | 125°C<br>Ripple<br>V<br>(100kHz) |
| CWR15 P/N                      | AVX MIL & COTS-Plus P/N        | AVX SRC9000 P/N                | Case | +25°C  | +85°C                               | +125°C                             | +25°C   | +85°C | +125°C | +25°C  | +85°C                             | +125°C |                           |                                 |                                 |                                  |                                 |                                 |                                  |
| CWR15CK685^L+                  | TBC L 685 * 004 C □ # @ 0 ^ +  | TBC L 685 * 004 C □ L @ 9 ^ +  | L    | 6.8  | 4                                   | 10                                 | 0.5     | 5     | 6      | 8      | 16                                | 12     | 0.025                     | 0.05                            | 0.05                            | 0.02                             | 0.50                            | 0.45                            | 0.20                             |
| CWR15CK106^R+                  | TBC R 106 * 004 C □ # @ 0 ^ ++ | TBC R 106 * 004 C □ L @ 9 ^ ++ | R    | 10   | 4                                   | 6                                  | 0.5     | 5     | 6      | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15CK156^R+                  | TBC R 156 * 004 C □ # @ 0 ^ ++ | TBC R 156 * 004 C □ L @ 9 ^ ++ | R    | 15   | 4                                   | 6                                  | 0.6     | 6     | 7      | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15CK226^R+                  | TBC R 226 * 004 C □ # @ 0 ^ ++ | TBC R 226 * 004 C □ L @ 9 ^ ++ | R    | 22   | 4                                   | 6                                  | 0.9     | 9     | 11     | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15CK336^R+                  | TBC R 336 * 004 C □ # @ 0 ^ ++ | TBC R 336 * 004 C □ L @ 9 ^ ++ | R    | 33   | 4                                   | 6                                  | 1.3     | 13    | 16     | 10     | 20                                | 15     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15CK686^A+                  | TBC A 686 * 004 C □ # @ 0 ^ +  | TBC A 686 * 004 C □ L @ 9 ^ +  | A    | 68   | 4                                   | 1                                  | 2.7     | 27    | 33     | 15     | 30                                | 23     | 0.040                     | 0.20                            | 0.18                            | 0.08                             | 0.20                            | 0.18                            | 0.08                             |
| CWR15DK335^L+                  | TBC L 335 * 006 C □ # @ 0 ^ +  | TBC L 335 * 006 C □ L @ 9 ^ +  | L    | 3.3  | 6                                   | 10                                 | 0.5     | 5     | 6      | 6      | 12                                | 9      | 0.025                     | 0.05                            | 0.05                            | 0.02                             | 0.50                            | 0.45                            | 0.20                             |
| CWR15DK475^L+                  | TBC L 475 * 006 C □ # @ 0 ^ +  | TBC L 475 * 006 C □ L @ 9 ^ +  | L    | 4.7  | 6                                   | 10                                 | 0.5     | 5     | 6      | 8      | 16                                | 12     | 0.025                     | 0.05                            | 0.05                            | 0.02                             | 0.50                            | 0.45                            | 0.20                             |
| CWR15DK685^R+                  | TBC R 685 * 006 C □ # @ 0 ^ ++ | TBC R 685 * 006 C □ L @ 9 ^ ++ | R    | 6.8  | 6                                   | 6                                  | 0.5     | 5     | 6      | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15DK106^R+                  | TBC R 106 * 006 C □ # @ 0 ^ ++ | TBC R 106 * 006 C □ L @ 9 ^ ++ | R    | 10   | 6                                   | 6                                  | 0.6     | 6     | 7      | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15DK156^R+                  | TBC R 156 * 006 C □ # @ 0 ^ ++ | TBC R 156 * 006 C □ L @ 9 ^ ++ | R    | 15   | 6                                   | 6                                  | 0.9     | 9     | 11     | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15DK226^A+                  | TBC A 226 * 006 C □ # @ 0 ^ +  | TBC A 226 * 006 C □ L @ 9 ^ +  | A    | 22   | 6                                   | 6                                  | 1.4     | 14    | 17     | 10     | 20                                | 15     | 0.040                     | 0.08                            | 0.07                            | 0.03                             | 0.49                            | 0.44                            | 0.20                             |
| CWR15DK336^A+                  | TBC A 336 * 006 C □ # @ 0 ^ +  | TBC A 336 * 006 C □ L @ 9 ^ +  | A    | 33   | 6                                   | 6                                  | 2       | 20    | 24     | 10     | 20                                | 15     | 0.040                     | 0.08                            | 0.07                            | 0.03                             | 0.49                            | 0.44                            | 0.20                             |
| CWR15DK476^A+                  | TBC A 476 * 006 C □ # @ 0 ^ +  | TBC A 476 * 006 C □ L @ 9 ^ +  | A    | 47   | 6                                   | 4                                  | 2.8     | 28    | 34     | 15     | 30                                | 23     | 0.040                     | 0.10                            | 0.09                            | 0.04                             | 0.40                            | 0.36                            | 0.16                             |
| CWR15FK474^L+                  | TBC L 474 * 010 C □ # @ 0 ^ +  | TBC L 474 * 010 C □ L @ 9 ^ +  | L    | 0.47   | 10                                  | 12                                 | 0.5     | 5     | 6      | 6      | 12                                | 9      | 0.025                     | 0.05                            | 0.04                            | 0.02                             | 0.55                            | 0.49                            | 0.22                             |
| CWR15FK684^L+                  | TBC L 684 * 010 C □ # @ 0 ^ +  | TBC L 684 * 010 C □ L @ 9 ^ +  | L    | 0.68   | 10                                  | 10                                 | 0.5     | 5     | 6      | 6      | 12                                | 9      | 0.025                     | 0.05                            | 0.05                            | 0.02                             | 0.50                            | 0.45                            | 0.20                             |
| CWR15FK105^L+                  | TBC L 105 * 010 C □ # @ 0 ^ +  | TBC L 105 * 010 C □ L @ 9 ^ +  | L    | 1  | 10                                  | 10                                 | 0.5     | 5     | 6      | 6      | 12                                | 9      | 0.025                     | 0.05                            | 0.05                            | 0.02                             | 0.50                            | 0.45                            | 0.20                             |
| CWR15FK155^L+                  | TBC L 155 * 010 C □ # @ 0 ^ +  | TBC L 155 * 010 C □ L @ 9 ^ +  | L    | 1.5  | 10                                  | 10                                 | 0.5     | 5     | 6      | 6      | 12                                | 9      | 0.025                     | 0.05                            | 0.05                            | 0.02                             | 0.50                            | 0.45                            | 0.20                             |
| CWR15FK225^L+                  | TBC L 225 * 010 C □ # @ 0 ^ +  | TBC L 225 * 010 C □ L @ 9 ^ +  | L    | 2.2  | 10                                  | 10                                 | 0.5     | 5     | 6      | 6      | 12                                | 9      | 0.025                     | 0.05                            | 0.05                            | 0.02                             | 0.50                            | 0.45                            | 0.20                             |
| CWR15FK335^R+                  | TBC R 335 * 010 C □ # @ 0 ^ +  | TBC R 335 * 010 C □ L @ 9 ^ +  | R    | 3.3  | 10                                  | 6                                  | 0.5     | 5     | 6      | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15FK475^R+                  | TBC R 475 * 010 C □ # @ 0 ^ +  | TBC R 475 * 010 C □ L @ 9 ^ +  | R    | 4.7  | 10                                  | 6                                  | 0.5     | 5     | 6      | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15FK685^R+                  | TBC R 685 * 010 C □ # @ 0 ^ +  | TBC R 685 * 010 C □ L @ 9 ^ +  | R    | 6.8  | 10                                  | 6                                  | 0.7     | 7     | 8.5    | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15FK106^R+                  | TBC R 106 * 010 C □ # @ 0 ^ +  | TBC R 106 * 010 C □ L @ 9 ^ +  | R    | 10   | 10                                  | 6                                  | 1       | 10    | 12     | 8      | 16                                | 12     | 0.045                     | 0.09                            | 0.08                            | 0.03                             | 0.52                            | 0.47                            | 0.21                             |
| CWR15FK156^R+                  | TBC A 156 * 010 C □ # @ 0 ^ +  | TBC A 156 * 010 C □ L @ 9 ^ +  | A    | 15   | 10                                  | 6                                  | 1.5     | 15    | 18     | 10     | 20                                | 15     | 0.040                     | 0.08                            | 0.07                            | 0.03                             | 0.49                            | 0.44                            | 0.20                             |
| CWR15JK474^R+                  | TBC L 474 * 020 C □ # @ 0 ^ +  | TBC L 474 * 020 C □ L @ 9 ^ +  | L    | 0.47   | 20                                  | 24                                 | 0.5     | 5     | 6      | 6      | 12                                | 9      | 0.025                     | 0.03                            | 0.03                            | 0.01                             | 0.77                            | 0.70                            | 0.31                             |


All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# TBC Series

## TBC COTS-Plus




TBC COTS-Plus series extends the range of CWR15. TBC is available with Weibull grade “B” reliability and all MIL-PRF-55365 Rev. G surge test options (“A”, “B” & “C”).

For Space Level applications, AVX SRC9000 ratings are available as shown in the rating table.

There are three termination finishes available: fused solder plated, gold plated, and 100% tin.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.




### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | EIA Metric | Length (L)   | Width (W)  | Height (H)   | Termination Spacing(S)    | Minimum Termination Length (Lt) | Average Mass |
|------|----------|------------|--|--|--|---------------------------|---------------------------------|--------------|
| A    | 1206     | 3216-18    | 3.20 ±0.20<br>(0.126 ±0.008)   | 1.60 ±0.20<br>(0.063 ±0.008)   | 1.60 ±0.20<br>(0.063 ±0.008)   | 1.80 min.<br>(0.071 min.) | 0.15<br>(0.006)                 | 44.6mg       |
| L    | 0603     | 1608-10    | 1.60 <sup>+0.25</sup> <sub>-0.15</sub><br>(0.063 <sup>+0.010</sup> <sub>-0.006</sub> ) | 0.84 <sup>+0.20</sup> <sub>-0.10</sub><br>(0.033 <sup>+0.008</sup> <sub>-0.004</sub> ) | 0.84 <sup>+0.20</sup> <sub>-0.10</sub><br>(0.033 <sup>+0.008</sup> <sub>-0.004</sub> ) | 0.55 min.<br>(0.022 min.) | 0.15<br>(0.006)                 | 8.6mg        |
| R    | 0805     | 2012-15    | 2.00 <sup>+0.25</sup> <sub>-0.15</sub><br>(0.079 <sup>+0.010</sup> <sub>-0.006</sub> ) | 1.35 <sup>+0.20</sup> <sub>-0.10</sub><br>(0.053 <sup>+0.008</sup> <sub>-0.004</sub> ) | 1.35 <sup>+0.20</sup> <sub>-0.10</sub><br>(0.053 <sup>+0.008</sup> <sub>-0.004</sub> ) | 0.70 min.<br>(0.027 min.) | 0.15<br>(0.006)                 | 29.9mg       |

### MARKING

#### A, L, R CASE



### CAPACITANCE AND RATED VOLTAGE, $V_R$ (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Voltage Rating DC ( $V_R$ ) at 85°C |      |     |     |     |     |
|-------------|------|-------------------------------------|------|-----|-----|-----|-----|
| μF          | Code | 4V                                  | 6.3V | 10V | 16V | 20V | 25V |
| 0.33        | 334  |                                     |      |     |     |     | L   |
| 0.47        | 474  |                                     |      | L   | L   | L   |     |
| 0.68        | 684  |                                     |      | L   | L   |     |     |
| 1.0         | 105  |                                     |      | L   |     |     |     |
| 1.5         | 155  |                                     |      | L   |     |     |     |
| 2.2         | 225  |                                     |      | L   |     |     |     |
| 3.3         | 335  |                                     |      | R   |     | R   |     |
| 4.7         | 475  |                                     | L    | R   | R   |     |     |
| 6.8         | 685  |                                     | R    | R   |     |     |     |
| 10          | 106  | R                                   | R    | R   | A   |     |     |
| 15          | 156  | R                                   |      | A   |     |     |     |
| 22          | 226  | R                                   | A    |     |     |     |     |
| 33          | 336  | R                                   | A    |     |     |     |     |
| 47          | 476  |                                     | A    |     |     |     |     |
| 68          | 686  | A                                   |      |     |     |     |     |

# TBC Series



## TBC COTS-Plus

### HOW TO ORDER

#### COTS-PLUS:

| TBC         | L                | 685   | *   | 004   | C   | □   | #  | @  | 0  | ^  | ++  |
|-------------|------------------|---|---|---|---|---|--|--|--|--|---|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>S = Std. Conformance<br>L = Group A | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf.<br>Z = Non-ER<br><br>None required | <b>Qualification Level</b><br>0 = N/A<br>9 = SRC9000 | <b>Termination Finish</b><br>0 = Fused Solder Plated<br>9 = Gold Plated<br>7 = Matte Sn (COTS-Plus only) | <b>Surge Test Option</b><br>00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 cycles, -55°C & +85°C before Weibull |



#### SPACE LEVEL OPTIONS TO SRC9000\*:

| TBC         | L                | 685   | *   | 004   | C  | □   | L                                      | @   | 9   | ^   | ++   |
|-------------|------------------|---|---|---|--|---|--|---|---|---|--|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Capacitance Tolerance</b><br>M = ±20%<br>K = ±10%<br>J = ±5% | <b>Voltage Code</b><br>004 = 4Vdc<br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc | <b>Standard or Low ESR Range</b><br>C = Std ESR<br>L = Low ESR | <b>Packaging</b><br>B = Bulk<br>R = 7" T&R<br>S = 13" T&R<br>W = Waffle<br><br>See page 8 for additional packaging options. | <b>Inspection Level</b><br>L = Group A | <b>Reliability Grade</b><br>Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf.<br>D = 0.001%/1000 hrs. 90% conf. | <b>Qualification Level</b><br>9 = SRC9000 | <b>Termination Finish</b><br>0 = Fused Solder Plated<br>9 = Gold Plated | <b>Surge Test Option</b><br>45 = 10 cycles, -55°C & +85°C before Weibull |



\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |  |     |     |    |    |    |    |  |
|------------------------------------|--|-----|-----|----|----|----|----|--|
| Technical Data:                    | All technical data relate to an ambient temperature of +25°C |     |     |    |    |    |    |  |
| Capacitance Range:                 | 0.33 µF to 68 µF   |     |     |    |    |    |    |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%  |     |     |    |    |    |    |  |
| Leakage Current DCL:               | 0.01CV or 0.5µA whichever is the greater                     |     |     |    |    |    |    |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ +85°C:   | 4   | 6.3 | 10 | 16 | 20 | 25 |  |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C:  | 2.7 | 4   | 7  | 10 | 13 | 17 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +85°C:   | 5.2 | 8   | 13 | 20 | 26 | 32 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +125°C:  | 3.2 | 5   | 8  | 12 | 16 | 20 |  |
| Temperature Range:                 | -55°C to +125°C  |     |     |    |    |    |    |  |

# TBC Series

## TBC COTS-Plus



| RATING & PART NUMBER REFERENCE          |                              |      |   | Parametric Specifications by Rating |                     |                 |         |       |        |        |             |       | Typical RMS Ripple Data by Rating |                |                |                 |                |                |                 |
|---|------------------------------|------|---|-------------------------------------|---------------------|-----------------|---------|-------|--------|--------|-------------|-------|-----------------------------------|----------------|----------------|-----------------|----------------|----------------|-----------------|
|   |                              |      |   | Cap<br>@ 120Hz                      | DC Rated<br>Voltage | ESR<br>@ 100kHz | DCL max |       |        | DF Max |             |       | Power<br>Dissipation              | 25°C<br>Ripple | 85°C<br>Ripple | 125°C<br>Ripple | 25°C<br>Ripple | 85°C<br>Ripple | 125°C<br>Ripple |
|   |                              |      |   |                                     |                     |                 | +25°C   | +85°C | +125°C | +25°C  | +(85/125)°C | -55°C |                                   |                |                |                 |                |                |                 |
| AVX P/N                                 | AVX SRC9000 P/N              | Case |   | μF<br>@ 25°C                        | V<br>@ +85°C        | Ohms<br>@ +25°C | (μA)    | (μA)  | (μA)   | (%)    | (%)         | (%)   | W                                 | A<br>(100kHz)  | A<br>(100kHz)  | V<br>(100kHz)   | V<br>(100kHz)  | V<br>(100kHz)  |                 |
| <b>4 Volt @ 85°C (2.7 Volt @ 125°C)</b> |                              |      |   |                                     |                     |                 |         |       |        |        |             |       |                                   |                |                |                 |                |                |                 |
| TBC R 106 * 004 C # @ 0 ^ ++            | TBC R 106 * 004 C L @ 9 ^ ++ | 0805 | R | 10                                  | 4.0                 | 6               | 0.5     | 5.0   | 6.3    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC R 156 * 004 C # @ 0 ^ ++            | TBC R 156 * 004 C L @ 9 ^ ++ | 0805 | R | 15                                  | 4.0                 | 6               | 0.6     | 6.0   | 7.5    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC R 226 * 004 C # @ 0 ^ ++            | TBC R 226 * 004 C L @ 9 ^ ++ | 0805 | R | 22                                  | 4.0                 | 6               | 0.9     | 8.8   | 11.0   | 15     | 30          | 23    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC R 336 * 004 C # @ 0 ^ ++            | TBC R 336 * 004 C L @ 9 ^ ++ | 0805 | R | 33                                  | 4.0                 | 6               | 1.3     | 13.2  | 16.5   | 10     | 20          | 15    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC A 686 * 004 C # @ 0 ^ ++            | TBC A 686 * 004 C L @ 9 ^ ++ | 1206 | A | 68                                  | 4.0                 | 1               | 2.7     | 27.2  | 34.0   | 15     | 30          | 23    | 0.040                             | 0.20           | 0.18           | 0.08            | 0.20           | 0.18           | 0.08            |
| <b>6.3 Volt @ 85°C (4 Volt @ 125°C)</b> |                              |      |   |                                     |                     |                 |         |       |        |        |             |       |                                   |                |                |                 |                |                |                 |
| TBC L 475 * 006 C # @ 0 ^ ++            | TBC L 475 * 006 C L @ 9 ^ ++ | 0603 | L | 4.7                                 | 6.3                 | 10              | 0.5     | 5.0   | 6.3    | 8      | 16          | 12    | 0.025                             | 0.05           | 0.05           | 0.02            | 0.50           | 0.45           | 0.20            |
| TBC R 685 * 006 C # @ 0 ^ ++            | TBC R 685 * 006 C L @ 9 ^ ++ | 0805 | R | 6.8                                 | 6.3                 | 6               | 0.5     | 5.0   | 6.3    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC R 106 * 006 C # @ 0 ^ ++            | TBC R 106 * 006 C L @ 9 ^ ++ | 0805 | R | 10                                  | 6.3                 | 6               | 0.6     | 6.3   | 7.9    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC A 226 K 006 C # @ 0 ^ ++            | TBC A 226 K 006 C L @ 9 ^ ++ | 1206 | A | 22                                  | 6.3                 | 6               | 1.4     | 13.9  | 17.3   | 10     | 20          | 15    | 0.040                             | 0.08           | 0.07           | 0.03            | 0.49           | 0.44           | 0.20            |
| TBC A 336 K 006 C # @ 0 ^ ++            | TBC A 336 K 006 C L @ 9 ^ ++ | 1206 | A | 33                                  | 6.3                 | 6               | 2.1     | 20.8  | 26.0   | 10     | 20          | 15    | 0.040                             | 0.08           | 0.07           | 0.03            | 0.49           | 0.44           | 0.20            |
| TBC A 476 * 006 C # @ 0 ^ ++            | TBC A 476 * 006 C L @ 9 ^ ++ | 1206 | A | 47                                  | 6.3                 | 1               | 3.0     | 29.6  | 37.0   | 15     | 30          | 23    | 0.040                             | 0.20           | 0.18           | 0.08            | 0.20           | 0.18           | 0.08            |
| <b>10 Volt @ 85°C (7 Volt @ 125°C)</b>  |                              |      |   |                                     |                     |                 |         |       |        |        |             |       |                                   |                |                |                 |                |                |                 |
| TBC L 474 * 010 C # @ 0 ^ ++            | TBC L 474 * 010 C L @ 9 ^ ++ | 0603 | L | 0.47                                | 10                  | 12              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.05           | 0.04           | 0.02            | 0.55           | 0.49           | 0.22            |
| TBC L 684 * 010 C # @ 0 ^ ++            | TBC L 684 * 010 C L @ 9 ^ ++ | 0603 | L | 0.68                                | 10                  | 10              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.05           | 0.05           | 0.02            | 0.50           | 0.45           | 0.20            |
| TBC L 105 * 010 C # @ 0 ^ ++            | TBC L 105 * 010 C L @ 9 ^ ++ | 0603 | L | 1.0                                 | 10                  | 10              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.05           | 0.05           | 0.02            | 0.50           | 0.45           | 0.20            |
| TBC L 155 * 010 C # @ 0 ^ ++            | TBC L 155 * 010 C L @ 9 ^ ++ | 0603 | L | 1.5                                 | 10                  | 10              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.05           | 0.05           | 0.02            | 0.50           | 0.45           | 0.20            |
| TBC L 225 * 010 C # @ 0 ^ ++            | TBC L 225 * 010 C L @ 9 ^ ++ | 0603 | L | 2.2                                 | 10                  | 10              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.05           | 0.05           | 0.02            | 0.50           | 0.45           | 0.20            |
| TBC R 335 * 010 C # @ 0 ^ ++            | TBC R 335 * 010 C L @ 9 ^ ++ | 0805 | R | 3.3                                 | 10                  | 6               | 0.5     | 5.0   | 6.3    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC R 475 * 010 C # @ 0 ^ ++            | TBC R 475 * 010 C L @ 9 ^ ++ | 0805 | R | 4.7                                 | 10                  | 6               | 0.5     | 4.7   | 5.9    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC R 685 * 010 C # @ 0 ^ ++            | TBC R 685 * 010 C L @ 9 ^ ++ | 0805 | R | 6.8                                 | 10                  | 6               | 0.7     | 6.8   | 8.5    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC R 106 * 010 C # @ 0 ^ ++            | TBC R 106 * 010 C L @ 9 ^ ++ | 0805 | R | 10                                  | 10                  | 6               | 1.0     | 10.0  | 12.5   | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC A 156 * 010 C # @ 0 ^ ++            | TBC A 156 * 010 C L @ 9 ^ ++ | 1206 | A | 15                                  | 10                  | 6               | 1.5     | 15.0  | 18.8   | 10     | 20          | 15    | 0.040                             | 0.08           | 0.07           | 0.03            | 0.49           | 0.44           | 0.20            |
| <b>16 Volt @ 85°C (10 Volt @ 125°C)</b> |                              |      |   |                                     |                     |                 |         |       |        |        |             |       |                                   |                |                |                 |                |                |                 |
| TBC L 474 * 016 C # @ 0 ^ ++            | TBC L 474 * 016 C L @ 9 ^ ++ | 0603 | L | 0.47                                | 16                  | 10              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.05           | 0.05           | 0.02            | 0.50           | 0.45           | 0.20            |
| TBC L 684 * 016 C # @ 0 ^ ++            | TBC L 684 * 016 C L @ 9 ^ ++ | 0603 | L | 0.68                                | 16                  | 10              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.05           | 0.05           | 0.02            | 0.50           | 0.45           | 0.20            |
| TBC R 475 * 016 C # @ 0 ^ ++            | TBC R 475 * 016 C L @ 9 ^ ++ | 0805 | R | 4.7                                 | 16                  | 6               | 0.8     | 7.5   | 9.0    | 10     | 20          | 15    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| TBC A 106 * 016 C # @ 0 ^ ++            | TBC A 106 * 016 C L @ 9 ^ ++ | 1206 | A | 10                                  | 16                  | 3               | 1.6     | 16.0  | 19.2   | 8      | 16          | 12    | 0.040                             | 0.12           | 0.10           | 0.05            | 0.20           | 0.18           | 0.08            |
| <b>20 Volt @ 85°C (13 Volt @ 125°C)</b> |                              |      |   |                                     |                     |                 |         |       |        |        |             |       |                                   |                |                |                 |                |                |                 |
| TBC L 474 * 020 C # @ 0 ^ ++            | TBC L 474 * 020 C L @ 9 ^ ++ | 0603 | L | 0.47                                | 20                  | 24              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.03           | 0.03           | 0.01            | 0.77           | 0.70           | 0.31            |
| TBC R 335 * 020 C # @ 0 ^ ++            | TBC R 335 * 020 C L @ 9 ^ ++ | 0805 | R | 3.3                                 | 20                  | 6               | 0.7     | 6.6   | 8.3    | 8      | 16          | 12    | 0.045                             | 0.09           | 0.08           | 0.03            | 0.52           | 0.47           | 0.21            |
| <b>25 Volt @ 85°C (17 Volt @ 125°C)</b> |                              |      |   |                                     |                     |                 |         |       |        |        |             |       |                                   |                |                |                 |                |                |                 |
| TBC L 334 M 025 C # @ 0 ^ ++            | TBC L 334 M 025 C L @ 9 ^ ++ | 0603 | L | 0.33                                | 25                  | 30              | 0.5     | 5.0   | 6.3    | 6      | 12          | 9     | 0.025                             | 0.03           | 0.03           | 0.01            | 0.87           | 0.78           | 0.35            |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# TBC Series



## HRC5000 Medical Implantable Grade




The TBC HRC5000 Medical Grade series is designed for use in medical implantable applications. These are some of the smallest surface mount tantalum capacitors available on the market which feature extremely low DC leakage limits well below typical values.



These components are manufactured and tested in the AVX Biddeford Maine factory which is ISO 13485 certified. Weibull grading and surge current testing options per MIL-PRF-55365 are available along with several plating options including tin/lead solder, 100% tin, or gold terminations.


To request a specific rating or for more information on HRC5000 testing details please contact the factory.

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.



### MARKING

#### A, B, L, R, S CASE



### CASE DIMENSIONS: millimeters (inches)

| Case Code | EIA Code | Length (L)   | Width (W)  | Height (H)   | Term. Width (P) min. |
|-----------|----------|--|--|--|----------------------|
| A         | 1206     | 3.20 ±0.20<br>(0.126 ±0.008)                                       | 1.60 ±0.20<br>(0.063 ±0.008)                                       | 1.60 ±0.20<br>(0.063 ±0.008)                                       | 0.15<br>(0.006)      |
| B         | 1411     | 3.60 ±0.20<br>(0.141 ±0.008)                                       | 2.90 ±0.15<br>(0.114 ±0.006)                                       | 1.50 max<br>(0.06 max)   | 0.15<br>(0.006)      |
| L         | 0603     | 1.60 <sup>+0.25</sup> <sub>-0.15</sub><br>+0.010<br>(0.063 -0.006) | 0.84 <sup>+0.20</sup> <sub>-0.10</sub><br>+0.008<br>(0.033 -0.004) | 0.84 <sup>+0.20</sup> <sub>-0.10</sub><br>+0.008<br>(0.033 -0.004) | 0.15<br>(0.006)      |
| R         | 0805     | 2.00 <sup>+0.25</sup> <sub>-0.15</sub><br>+0.010<br>(0.079 -0.006) | 1.35 <sup>+0.20</sup> <sub>-0.10</sub><br>+0.008<br>(0.053 -0.004) | 1.35 <sup>+0.20</sup> <sub>-0.10</sub><br>+0.008<br>(0.053 -0.004) | 0.15<br>(0.006)      |
| S         | 1207     | 3.20 ±0.20<br>(0.126 ±0.008)                                       | 1.80 ±0.20<br>(0.071 ±0.008)                                       | 1.50 max<br>(0.06 max)   | 0.15<br>(0.006)      |

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage |    |     |           |     |     |
|-------------|------|---------------|----|-----|-----------|-----|-----|
| µF          | Code | 4V            | 6V | 10V | 16V       | 20V | 40V |
| 0.47        | 474  |               |    | L   |           |     |     |
| 0.68        | 684  |               |    |     |           |     |     |
| 1           | 105  |               |    | L   |           | R   | A   |
| 1.5         | 155  |               |    |     |           |     |     |
| 2.2         | 225  |               |    | L   |           |     |     |
| 3.3         | 335  |               | L  | R   |           |     |     |
| 4.7         | 475  |               |    | R   | R         |     |     |
| 6.8         | 685  |               |    | R   |           |     |     |
| 10          | 106  |               |    | R   | R/A (17v) |     |     |
| 15          | 156  | R             |    |     |           |     |     |
| 22          | 226  |               |    |     |           |     |     |
| 33          | 336  |               |    |     |           |     |     |
| 47          | 476  |               | S  | B   |           |     |     |



# TBC Series



## HRC5000 Medical Implantable Grade

### HOW TO ORDER

| TBC         | R                | 106  | *                               | 010   | C           | □                                    | L                       | @   | 5                          | ^   | ++  |
|-------------|------------------|--|---------------------------------|---|-------------|--------------------------------------|-------------------------|---|----------------------------|---|---|
| <b>Type</b> | <b>Case Size</b> | <b>Capacitance Code</b>  | <b>Capacitance Tolerance</b>    | <b>Voltage Code</b>   | <b>ESR</b>  | <b>Packaging</b>                     | <b>Inspection Level</b> | <b>Reliability Grade</b>  | <b>Qualification Level</b> | <b>Termination Finish</b>                           | <b>Surge Test Option</b>  |
|             |                  | pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | J = ±5%<br>K = ±10%<br>M = ±20% | 004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>017 = 17Vdc<br>020 = 20Vdc<br>040 = 40Vdc | C = Std ESR | B = Bulk<br>R = 7* T&R<br>W = Waffle | L = Group A             | Weibull:<br>B = 0.1%/1000 hrs. 90% conf.<br>C = 0.01%/1000 hrs. 90% conf. | 5 = HRC5000                | 0 = Solder Fused<br>9 = Gold Plated<br>7 = 100% Tin | 00 = None<br>23 = 10 Cycles, +25°C<br>24 = 10 Cycles, -55°C & +85°C<br>45 = 10 Cycles, -55°C & +85°C before Weibull |



\*Contact factory for AVX HRC5000 Medical Grade SCD details.

### TECHNICAL SPECIFICATIONS

Technical Data: Unless otherwise specified, all technical data relate to an ambient temperature of 25°C

|                                    |                  |     |     |      |      |      |      |  |
|------------------------------------|------------------|-----|-----|------|------|------|------|--|
| Capacitance Range:                 | 0.47 μF to 47 μF |     |     |      |      |      |      |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%  |     |     |      |      |      |      |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ +85°C:         | 4   | 6   | 10   | 16   | 20   | 40   |  |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C:        | 2.7 | 4   | 6.7  | 10.7 | 13.3 | 26.7 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +85°C:         | 5.3 | 8   | 13.3 | 20.8 | 26.7 | 52   |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +125°C:        | 3.5 | 5.3 | 8.7  | 13.9 | 17.8 | 34.7 |  |
| Temperature Range:                 | -55°C to +125°C  |     |     |      |      |      |      |  |

# TBC Series



## HRC5000 Medical Implantable Grade

| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating |                  |              |         |        |        |        |           |       | Typical RMS Ripple Data by Rating |                     |                     |                      |                     |                     |                      |
|--------------------------------|------|-------------------------------------|------------------|--------------|---------|--------|--------|--------|-----------|-------|-----------------------------------|---------------------|---------------------|----------------------|---------------------|---------------------|----------------------|
|                                |      | Cap @ 120Hz                         | DC Rated Voltage | ESR @ 100kHz | DCL max |        |        | DF max |           |       | Power Dissipation                 | 25°C Ripple Current | 85°C Ripple Current | 125°C Ripple Current | 25°C Ripple Voltage | 85°C Ripple Voltage | 125°C Ripple Voltage |
|                                |      |                                     |                  |              | +25°C   | +85°C  | +125°C | +25°C  | +85/125°C | -55°C |                                   |                     |                     |                      |                     |                     |                      |
| AVX HRC5000 P/N                | Case | µF @ 25°C                           | V @ +85°C        | Ohms @ +25°C | (µA)    | (µA)   | (µA)   | (%)    | (%)       | (%)   |                                   |                     |                     |                      |                     |                     |                      |
| TBCR156*004C□L@5^++            | R    | 15                                  | 4                | 6            | 0.150   | 1.500  | 1.800  | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.522               | 0.468               | 0.210                |
| TBCL335*006C□L@5^++            | L    | 3.3                                 | 6                | 10           | 0.100   | 1.000  | 1.200  | 6      | 12        | 9     | 0.025                             | 0.05                | 0.045               | 0.02                 | 0.500               | 0.450               | 0.200                |
| TBCS476*006C□L@5^++            | S    | 47                                  | 6                | 4            | 0.470   | 4.700  | 5.640  | 6      | 8         | 9     | 0.04                              | 0.1                 | 0.09                | 0.04                 | 0.400               | 0.360               | 0.160                |
| TBCL474*010C□L@5^++            | L    | 0.47                                | 10               | 12           | 0.100   | 1.000  | 1.200  | 6      | 12        | 9     | 0.025                             | 0.046               | 0.041               | 0.018                | 0.552               | 0.492               | 0.216                |
| TBCL105*010C□L@5^++            | L    | 1                                   | 10               | 10           | 0.100   | 1.000  | 1.200  | 6      | 12        | 9     | 0.025                             | 0.05                | 0.045               | 0.02                 | 0.500               | 0.450               | 0.200                |
| TBCL225*010C□L@5^++            | L    | 2.2                                 | 10               | 10           | 0.100   | 1.000  | 1.200  | 6      | 12        | 9     | 0.025                             | 0.05                | 0.045               | 0.02                 | 0.500               | 0.450               | 0.200                |
| TBCR335*010C□L@5^++            | R    | 3.3                                 | 10               | 6            | 0.100   | 1.000  | 1.200  | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.522               | 0.468               | 0.210                |
| TBCR475*010C□L@5^++            | R    | 4.7                                 | 10               | 6            | 0.118   | 1.175  | 1.410  | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.522               | 0.468               | 0.210                |
| TBCR685*010C□L@5^++            | R    | 6.8                                 | 10               | 6            | 0.170   | 1.700  | 2.040  | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.522               | 0.468               | 0.210                |
| TBCR106*010C□L@5^++            | R    | 10                                  | 10               | 6            | 0.250   | 2.500  | 3.000  | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.522               | 0.468               | 0.210                |
| TBCB476*010C□L@5^++            | B    | 47                                  | 10               | 1            | 1.175   | 11.750 | 14.100 | 15     | 30        | 23    | 0.04                              | 0.2                 | 0.18                | 0.08                 | 0.200               | 0.180               | 0.080                |
| TBCR475*016C□L@5^++            | R    | 4.7                                 | 16               | 6            | 0.188   | 1.880  | 2.256  | 8      | 10        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.522               | 0.468               | 0.210                |
| TBCR106*016C□L@5^++            | R    | 10                                  | 16               | 5            | 0.400   | 4.000  | 4.800  | 8      | 16        | 12    | 0.045                             | 0.095               | 0.085               | 0.038                | 0.475               | 0.425               | 0.190                |
| TBCA106*017C□L@5^++            | A    | 10                                  | 17               | 3            | 0.425   | 4.250  | 5.100  | 8      | 16        | 12    | 0.04                              | 0.115               | 0.104               | 0.046                | 0.345               | 0.312               | 0.138                |
| TBCR105*020C□L@5^++            | R    | 1                                   | 20               | 6            | 0.100   | 1.000  | 1.200  | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.522               | 0.468               | 0.210                |
| TBCA105*040C□L@5^++            | A    | 1                                   | 40               | 6            | 0.100   | 1.000  | 1.200  | 8      | 16        | 12    | 0.04                              | 0.082               | 0.073               | 0.033                | 0.492               | 0.438               | 0.198                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

## HRC6000 Medical Implantable Grade



The TBC HRC6000 Medical Grade series is the next generation of our internally qualified medical grade tantalum capacitors. These components are screened using our newly designed Q-Process to effectively remove components that may experience parametric shifts through customer processing or display instability through life testing.




Due to the deficiencies of Weibull grading and its tendency to Burn-In potentially unstable units, this Q-Process utilizes a Product Level Designation system based on a simulated production routine performed on a sample from the population. Once that is completed a calculation is done based on the performance of the sample which can take into account the application conditions of the end customer. This system also allows for derating recommendations to be relaxed as illustrated by the section below.

These components are manufactured and tested in the AVX Biddeford Maine factory which is ISO 13485 certified. For more information on this process or to request a specific rating please contact the factory. In addition, DC leakage testing at application voltage is available upon request.


For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)

For moisture sensitivity levels please refer to the High Reliability Tantalum MSL section located in the back of the High Reliability Tantalum Catalog.



### MARKING

#### A, B, L, R, S CASE



### CASE DIMENSIONS: millimeters (inches)

| Case Code | EIA Code | Length (L)  | Width (W)   | Height (H)  | Term. Width (P) min. |
|-----------|----------|---|---|---|----------------------|
| A         | 1206     | 3.20 ±0.20<br>(0.126 ±0.008)  | 1.60 ±0.20<br>(0.063 ±0.008)  | 1.60 ±0.20<br>(0.063 ±0.008)  | 0.15<br>(0.006)      |
| B         | 1411     | 3.60 ±0.20<br>(0.141 ±0.008)  | 2.90 ±0.15<br>(0.114 ±0.006)  | 1.50 max<br>(0.06 max)  | 0.15<br>(0.006)      |
| L         | 0603     | 1.60 <sup>+0.25</sup> <sub>-0.15</sub><br><sup>+0.010</sup> <sub>-0.006</sub><br>(0.063 ±0.006) | 0.84 <sup>+0.20</sup> <sub>-0.10</sub><br><sup>+0.008</sup> <sub>-0.004</sub><br>(0.033 ±0.004) | 0.84 <sup>+0.20</sup> <sub>-0.10</sub><br><sup>+0.008</sup> <sub>-0.004</sub><br>(0.033 ±0.004) | 0.15<br>(0.006)      |
| R         | 0805     | 2.00 <sup>+0.25</sup> <sub>-0.15</sub><br><sup>+0.010</sup> <sub>-0.006</sub><br>(0.079 ±0.006) | 1.35 <sup>+0.20</sup> <sub>-0.10</sub><br><sup>+0.008</sup> <sub>-0.004</sub><br>(0.053 ±0.004) | 1.35 <sup>+0.20</sup> <sub>-0.10</sub><br><sup>+0.008</sup> <sub>-0.004</sub><br>(0.053 ±0.004) | 0.15<br>(0.006)      |
| S         | 1207     | 3.20 ±0.20<br>(0.126 ±0.008)  | 1.80 ±0.20<br>(0.071 ±0.008)  | 1.50 max<br>(0.06 max)  | 0.15<br>(0.006)      |

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage |      |     |
|-------------|------|---------------|------|-----|
| μF          | Code | 4V            | 6V   | 10V |
| 2.2         | 225  |               |      | L   |
| 3.3         | 335  |               | L    |     |
| 4.7         | 475  |               | L    |     |
| 6.8         | 685  |               |      | R   |
| 10          | 106  | L             |      | R   |
| 15          | 156  |               | R    |     |
| 22          | 226  |               | R    |     |
| 33          | 336  |               | S    | B   |
| 47          | 476  |               | A, S | B   |
| 68          | 686  | S             | B    |     |



# TBC Series



## HRC6000 Medical Implantable Grade

### HOW TO ORDER

| TBC  | R         | 106  | *  | 010   | C                  | □   | L                               | Q  | 6                                  | ^   | ++                        |
|------|-----------|--|--|---|--------------------|---|---------------------------------|--|------------------------------------|---|---------------------------|
| Type | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>J = ±5%<br>K = ±10%<br>M = ±20% | Voltage Code<br>004 = 4Vdc<br>006 = 6Vdc<br>010 = 10Vdc | ESR<br>C = Std ESR | Packaging<br>B = Bulk<br>R = 7" T&R<br>W = Waffle | Inspection Level<br>L = Group A | Reliability Grade<br>Product Level<br>Designator:<br>Q = 0.1%/1000 Hours<br>Minimum, 60% conf. | Qualification Level<br>6 = HRC6000 | Termination Finish<br>0 = Solder Fused<br>9 = Gold Plated<br>7 = 100% Matte Tin | Custom Option<br>00 = Std |

LEAD-FREE  
LEAD-FREE COMPATIBLE  
COMPONENT

RoHS  
COMPLIANT

For RoHS compliant products,  
please select correct termination style.

\*Contact factory for AVX HRC6000 Medical Grade SCD details.

### TECHNICAL SPECIFICATIONS

|                                    |  |     |   |     |  |
|------------------------------------|--|-----|---|-----|--|
| Technical Data:                    | Unless otherwise specified, all technical data relate to an ambient temperature of +25°C |     |   |     |  |
| Capacitance Range:                 | 2.2 μF to 68 μF  |     |   |     |  |
| Capacitance Tolerance:             | ±5%; ±10%; ±20%  |     |   |     |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ +85°C:   | 4   | 6 | 10  |  |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C:  | 2.7 | 4 | 6.7 |  |
| Temperature Range:                 | -55°C to +125°C  |     |   |     |  |

# TBC Series



## HRC6000 Medical Implantable Grade

| RATING & PART NUMBER REFERENCE |      | Parametric Specifications by Rating |                  |              |         |       |        |        |           |       | Typical RMS Ripple Data by Rating |                     |                     |                      |                     |                     |                      |
|--------------------------------|------|-------------------------------------|------------------|--------------|---------|-------|--------|--------|-----------|-------|-----------------------------------|---------------------|---------------------|----------------------|---------------------|---------------------|----------------------|
|                                |      | Cap @ 120Hz                         | DC Rated Voltage | ESR @ 100kHz | DCL max |       |        | DF max |           |       | Power Dissipation                 | 25°C Ripple Current | 85°C Ripple Current | 125°C Ripple Current | 25°C Ripple Voltage | 85°C Ripple Voltage | 125°C Ripple Voltage |
|                                |      |                                     |                  |              | +25°C   | +85°C | +125°C | +25°C  | +85/125°C | -55°C |                                   |                     |                     |                      |                     |                     |                      |
| AVX HRC6000 P/N                | Case | µF @ 25°C                           | V @ +85°C        | Ohms @ +25°C | (µA)    | (µA)  | (µA)   | (%)    | (%)       | (%)   | W                                 | A (100kHz)          | A (100kHz)          | A (100kHz)           | V (100kHz)          | V (100kHz)          | V (100kHz)           |
| TBCL106*004C□LQ6^++            | L    | 10                                  | 4                | 10           | 0.100   | 1.00  | 1.20   | 8      | 16        | 12    | 0.025                             | 0.050               | 0.045               | 0.020                | 0.500               | 0.450               | 0.200                |
| TBCS686*004C□LQ6^++            | S    | 68                                  | 4                | 4            | 0.680   | 6.80  | 8.16   | 15     | 30        | 23    | 0.040                             | 0.100               | 0.090               | 0.040                | 0.400               | 0.360               | 0.160                |
| TBCL335*006C□LQ6^++            | L    | 3.3                                 | 6                | 10           | 0.050   | 0.50  | 0.60   | 6      | 12        | 9     | 0.025                             | 0.050               | 0.045               | 0.020                | 0.500               | 0.450               | 0.200                |
| TBCL475*006C□LQ6^++            | L    | 4.7                                 | 6                | 10           | 0.071   | 0.71  | 0.852  | 8      | 16        | 12    | 0.025                             | 0.050               | 0.045               | 0.020                | 0.500               | 0.450               | 0.200                |
| TBCR156*006C□LQ6^++            | R    | 15                                  | 6                | 6            | 0.225   | 2.25  | 2.70   | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.520               | 0.468               | 0.208                |
| TBCR226*006C□LQ6^++            | R    | 22                                  | 6                | 5            | 0.330   | 3.30  | 3.96   | 8      | 20        | 15    | 0.045                             | 0.095               | 0.085               | 0.038                | 0.474               | 0.427               | 0.190                |
| TBCS336*006C□LQ6^++            | S    | 33                                  | 6                | 6            | 0.495   | 4.95  | 5.94   | 8      | 16        | 12    | 0.040                             | 0.082               | 0.073               | 0.033                | 0.490               | 0.441               | 0.196                |
| TBCA476*006C□LQ6^++            | A    | 47                                  | 6                | 4            | 0.705   | 7.05  | 8.46   | 15     | 30        | 23    | 0.040                             | 0.100               | 0.090               | 0.040                | 0.400               | 0.360               | 0.160                |
| TBCS476*006C□LQ6^++            | S    | 47                                  | 6                | 4            | 0.705   | 7.05  | 8.46   | 8      | 16        | 12    | 0.040                             | 0.100               | 0.090               | 0.040                | 0.400               | 0.360               | 0.160                |
| TBCB686*006C□LQ6^++            | B    | 68                                  | 6                | 1            | 1.020   | 10.20 | 12.24  | 15     | 30        | 22.5  | 0.040                             | 0.200               | 0.180               | 0.080                | 0.200               | 0.180               | 0.080                |
| TBCL225*010C□LQ6^++            | L    | 2.2                                 | 10               | 10           | 0.055   | 0.55  | 0.66   | 6      | 12        | 9     | 0.025                             | 0.050               | 0.045               | 0.020                | 0.500               | 0.450               | 0.200                |
| TBCR685*010C□LQ6^++            | R    | 6.8                                 | 10               | 6            | 0.170   | 1.70  | 2.04   | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.520               | 0.468               | 0.208                |
| TBCR106*010C□LQ6^++            | R    | 10                                  | 10               | 6            | 0.250   | 2.50  | 3.00   | 8      | 16        | 12    | 0.045                             | 0.087               | 0.078               | 0.035                | 0.520               | 0.468               | 0.208                |
| TBCB336*010C□LQ6^++            | B    | 33                                  | 10               | 1            | 0.825   | 8.25  | 9.90   | 15     | 30        | 22.5  | 0.040                             | 0.200               | 0.180               | 0.080                | 0.200               | 0.180               | 0.080                |
| TBCB476*010C□LQ6^++            | B    | 47                                  | 10               | 1            | 1.175   | 11.75 | 14.1   | 15     | 30        | 22.5  | 0.040                             | 0.200               | 0.180               | 0.080                | 0.200               | 0.180               | 0.080                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

## HRC6000 DERATING GUIDELINES


Due to our new Q-Process test procedures the need for a typical 50% derating of the capacitors rated voltage in application can be relaxed. Below is a table outlining some of the common applications where these components are utilized along with appropriate derating recommendations. When determining the appropriate capacitor voltage rating to utilize, the application voltage is determined by the maximum D.C. voltage with the addition of any A.C. ripple voltage that may be present.

| Recommended Derating | Application |
|----------------------|-------------|
| 20%                  | Filtering   |
| 0%                   | Pacing      |
| 0%                   | Hold-Up     |
| 0%                   | Charging    |

# T4C – Microchip Medical Series



## HRC4000 Implantable Non Life Support and Non Implantable Life Support



The AVX T4C microchip medical series is designed for use in Implantable - Non-Life support or Non-Implantable - Life support medical applications with space limits. These components are screened using our newly designed Q-Process to effectively remove components that may experience parametric shifts through customer processing or display instability through life testing.

### FEATURES

- Dedicated to medical applications
- HRC4000 - Implantable, Non-Life support  
- Non-Implantable, Life support
- -55 to +125°C operation temperature
- Basic reliability better than 0.1%/1000hours
- Custom DCL / ESR options on selected parts



For RoHS compliant products, please select correct termination style.


T4C Standard - Standard option DCL and ESR limits including Q-Process screening.

T4C Custom – A custom option where specific DCL and ESR parameter limits can be agreed based Q-Process statistical screening. DCL down to 0.005CV on selected codes

### APPLICATIONS


- Medical, Implantable - Non-Life support and Non-Implantable - Life support

For additional information on Q-process please consult the AVX technical publication “Reaching the Highest Reliability for Tantalum Capacitors” (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)



### MARKING

#### K, L, R CASE



### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | EIA Metric | L+0.20 (0.008)<br>-0.00 (0.000) | W+0.15 (0.006)<br>-0.00 (0.000)                 | H+0.15 (0.006)<br>-0.00 (0.000)                 | Termination Spacing(S) | Minimum Termination Length (Lt) |
|------|----------|------------|---------------------------------|---|---|------------------------|---------------------------------|
| K    | 0402     | 1005-07    | 1.00 (0.039)                    | 0.50 +0.20<br>-0.00<br>(0.020 +0.008<br>-0.000) | 0.50 +0.20<br>-0.00<br>(0.020 +0.008<br>-0.000) | 0.40 (0.016) min       | 0.10 (0.004)                    |
| L    | 0603     | 1608-10    | 1.60 (0.063)                    | 0.85 (0.033)                                    | 0.85 (0.033)                                    | 0.55 (0.022) min       | 0.15 (0.006)                    |
| R    | 0805     | 2012-15    | 2.00 (0.079)                    | 1.35 (0.053)                                    | 1.35 (0.053)                                    | 0.70 (0.028) min       | 0.15 (0.006)                    |

### CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) to 85°C (Voltage Code) |          |                     |         |
|-------------|------|---|----------|---------------------|---------|
| µF          | Code | 4V (G)  | 6.3V (J) | 10V (A)             | 16V (C) |
| 0.33        | 334  |   |          |                     |         |
| 0.47        | 474  |   |          | K                   |         |
| 1.0         | 105  | K   | K        | L                   | L       |
| 2.2         | 225  |   |          | L                   |         |
| 3.3         | 335  |   |          |                     |         |
| 4.7         | 475  | K   |          |                     |         |
| 10          | 106  |   |          | L <sup>(M)</sup> ,R |         |
| 15          | 156  |   |          |                     |         |
| 22          | 226  |   | R        |                     |         |

Available Ratings (M tolerance only)

Please contact the factory for codes not listed in the table.

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards with customer written approval.



# T4C – Microchip Medical Series



## HRC4000 Implantable Non Life Support and Non Implantable Life Support

### HOW TO ORDER

|            |           |   |                       |  |                           |  |                    |                         |                     |   |                              |
|------------|-----------|---|-----------------------|--|---------------------------|--|--------------------|-------------------------|---------------------|---|------------------------------|
| <b>T4C</b> | <b>K</b>  | <b>105</b>  | <b>*</b>              | <b>006</b>   | <b>C</b>                  | <b>□</b>   | <b>L</b>           | <b>Q</b>                | <b>4</b>            | <b>^</b>  | <b>00</b>                    |
| Type       | Case Size | Capacitance Code  | Capacitance Tolerance | Voltage Code   | Standard or Low ESR Range | Packaging  | Inspection Level   | Reliability Grade       | Qualification Level | Termination Finish  | Suffix                       |
|            |           | pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | M = ±20%<br>K = ±10%  | 004 = 4Vdc<br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc | C = Std ESR               | R, P = 7" Reel<br>X, Q = 4 1/4" Reel<br>B = Bulk | L = Lab Inspection | Q = Q-Process Screening | 4 = HRC4000         | 7 = 100% Tin<br>9 = Gold Plated<br>H = SnPb Non RoHS<br>H, 9 = (Contact Manufacturer) | 00 = Standard<br>XX = Custom |

### TECHNICAL SPECIFICATIONS

|                                    |  |     |     |     |    |
|------------------------------------|--|-----|-----|-----|----|
| Technical Data:                    | All technical data relate to an ambient temperature of +25°C                                   |     |     |     |    |
| Capacitance Range:                 | 0.47 µF to 22 µF (for extended range contact manufacturer)                                     |     |     |     |    |
| Capacitance Tolerance:             | ±10%; ±20%   |     |     |     |    |
| Leakage Current DCL:               | 0.01CV or 0.3µA whichever is the greater   |     |     |     |    |
| Rated Voltage (V <sub>R</sub> )    | ≤ +85°C:   | 4   | 6.3 | 10  | 16 |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C:  | 2.7 | 4   | 6.7 | 10 |
| Surge Voltage (V <sub>S</sub> )    | ≤ +85°C:   | 5.2 | 8   | 13  | 20 |
| Surge Voltage (V <sub>S</sub> )    | ≤ +125°C:  | 3.2 | 5   | 8   | 13 |
| Temperature Range:                 | -55°C to +125°C  |     |     |     |    |
| Reliability:                       | 0.1% per 1000 hours at 25°C, V <sub>R</sub> with 0.1Ω/V series impedance, 90% confidence level |     |     |     |    |

### RATINGS & PART NUMBER REFERENCE

| AVX Part No.           | Case Size | Capacitance (µF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (µA) | DF Max. (%) | ESR Max. @ 100kHz (Ω) | MSL | 100kHz RMS Current (mA) |      |       |
|------------------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|-----------------------|-----|-------------------------|------|-------|
|                        |           |                  |                   |                        |                      |                           |               |             |                       |     | 25°C                    | 85°C | 125°C |
| <b>4 Volt @ 85°C</b>   |           |                  |                   |                        |                      |                           |               |             |                       |     |                         |      |       |
| T4CK105*004C□LQ4^00    | K         | 1                | 4                 | 85                     | 2.7                  | 125                       | 0.3           | 6           | 15                    | 3   | 32                      | 28   | 13    |
| T4CK475*004C□LQ4^00    | K         | 4.7              | 4                 | 85                     | 2.7                  | 125                       | 0.3           | 20          | 15                    | 3   | 32                      | 28   | 13    |
| <b>6.3 Volt @ 85°C</b> |           |                  |                   |                        |                      |                           |               |             |                       |     |                         |      |       |
| T4CK105*006C□LQ4^00    | K         | 1                | 6.3               | 85                     | 4                    | 125                       | 0.3           | 6           | 15                    | 3   | 32                      | 28   | 13    |
| T4CR226*006C□LQ4^00    | R         | 22               | 6.3               | 85                     | 4                    | 125                       | 1.4           | 10          | 5                     | 3   | 95                      | 85   | 38    |
| <b>10 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                       |     |                         |      |       |
| T4CK474*010C□LQ4^00    | K         | 0.47             | 10                | 85                     | 6.7                  | 125                       | 0.3           | 6           | 15                    | 3   | 32                      | 28   | 13    |
| T4CL105*010C□LQ4^00    | L         | 1                | 10                | 85                     | 6.7                  | 125                       | 0.3           | 6           | 7.5                   | 3   | 58                      | 52   | 23    |
| T4CL225*010C□LQ4^00    | L         | 2.2              | 10                | 85                     | 6.7                  | 125                       | 0.3           | 6           | 7.5                   | 3   | 58                      | 52   | 23    |
| T4CL106M010C□LQ4^00    | L         | 10               | 10                | 85                     | 6.7                  | 125                       | 1             | 20          | 7.5                   | 3   | 58                      | 52   | 23    |
| T4CR106*010C□LQ4^00    | R         | 10               | 10                | 85                     | 6.7                  | 125                       | 1             | 8           | 5                     | 3   | 95                      | 85   | 38    |
| <b>16 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                       |     |                         |      |       |
| T4CL105*016C□LQ4^00    | L         | 1                | 16                | 85                     | 10                   | 125                       | 0.3           | 6           | 7.5                   | 3   | 58                      | 52   | 23    |

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts.

DCL is measured at rated voltage after 5 minutes.

The EIA & CECC standards for low ESR Solid Tantalum Capacitors allow an ESR movement to 1.25 times catalogue limit post mounting.

# T4C – Microchip Medical Series



## HRC4000 Implantable Non Life Support and Non Implantable Life Support

### QUALIFICATION TABLE

| TEST                  | T4C HRC4000 (Temperature range -55°C to +125°C)  |               |               |                    |                              |            |           |            |            |            |            |
|-----------------------|--|---------------|---------------|--------------------|------------------------------|------------|-----------|------------|------------|------------|------------|
|                       | Condition  |               |               | Characteristics    |                              |            |           |            |            |            |            |
| Endurance             | Determine after application of rated voltage for 2000 +48/-0 hours at 85±2°C and then leaving 1-2 hours at room temperature. Also determine of 125°C temperature, category voltage for 2000 +48/-0 hours and then leaving 1-2 hours at room temperature. Power supply impedance to be ≤0.1Ω/V. |               |               | Visual examination | no visible damage            |            |           |            |            |            |            |
|                       |  |               |               | DCL                | 1.25 x initial limit         |            |           |            |            |            |            |
|                       |  |               |               | ΔC/C               | within ±10% of initial value |            |           |            |            |            |            |
|                       |  |               |               | DF                 | initial limit                |            |           |            |            |            |            |
|                       |  |               |               | ESR                | 1.25 x initial limit         |            |           |            |            |            |            |
| Storage Life          | 125°C, 0V, 2000h   |               |               | Visual examination | no visible damage            |            |           |            |            |            |            |
|                       |  |               |               | DCL                | 1.25 x initial limit         |            |           |            |            |            |            |
|                       |  |               |               | ΔC/C               | within ±10% of initial value |            |           |            |            |            |            |
|                       |  |               |               | DF                 | initial limit                |            |           |            |            |            |            |
|                       |  |               |               | ESR                | 1.25 x initial limit         |            |           |            |            |            |            |
| Temperature Stability | Step   | Temperature°C | Duration(min) |                    | +20°C                        | -55°C      | +20°C     | +85°C      | +125°C     | +20°C      |            |
|                       | 1  | +20±2         | 15            | DCL                | IL*                          | n/a        | IL*       | 10 x IL*   | 12.5 x IL* | IL*        |            |
|                       | 2  | -55+0/-3      | 15            |                    | ΔC/C                         | n/a        | +0/-10%   | ±5%        | +10/-0%    | +12/-0%    | ±5%        |
|                       | 3  | +20±2         | 15            | DF                 |                              | IL*        | 1.5 x IL* | IL*        | 1.5 x IL*  | 2 x IL*    | IL*        |
|                       | 4  | +85+3/-0      | 15            |                    | ESR                          | 1.25 x IL* | 2.5 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* |
|                       | 5  | +125+3/-0     | 15            |                    |                              |            |           |            |            |            |            |
|                       | 6  | +20±2         | 15            |                    |                              |            |           |            |            |            |            |
| Surge Voltage         | Test temperature: 85°C+3/0°C<br>Test voltage: Rated voltage at 85°C<br>Surge voltage: 1.3x rated voltage at 85°C<br>Series protection resistance 1000±100Ω<br>Discharge resistance: 1000Ω<br>Number of cycles: 1000x<br>Cycle duration: 6 min; 30 sec charge,<br>5 min 30 sec discharge        |               |               | Visual examination | no visible damage            |            |           |            |            |            |            |
|                       |  |               |               | DCL                | initial limit                |            |           |            |            |            |            |
|                       |  |               |               | ΔC/C               | within ±5% of initial value  |            |           |            |            |            |            |
|                       |  |               |               | DF                 | initial limit                |            |           |            |            |            |            |
|                       |  |               |               | ESR                | 1.25 x initial limit         |            |           |            |            |            |            |

\*Initial Limit

### LOT ACCEPTANCE TESTING


| TEST                | T4C HRC4000 (Temperature range -55°C to +125°C)   |                    |                             |
|---------------------|---|--------------------|-----------------------------|
|                     | Condition   | Characteristics    |                             |
| Lot Acceptance Test | 25 Pieces from each lot<br>• Read and Record Initial Electricals<br>• Bake Out @ 125°C for 2 Hours<br>• Mount using AVX recommended profile<br>• Read and Record Post Mounting Electricals<br>• Life Test: 6 hours, 2/3 R.V., 125°C<br>• Read and Record Post Electricals | DCL                | initial limit               |
|                     |   | ΔC/C               | within ±5% of initial value |
|                     |   | DF                 | initial limit               |
|                     |   | ESR                | 1.25 x initial limit        |
|                     |   | 0 Failures Allowed |                             |



# TCB Series



## COTS-Plus Polymer Capacitor



The TCB series is a COTS-Plus version of the professional grade TCR polymer series.



### FEATURES

- Robust design for long operation lifetime
- AVX Q-process with statistical screening
- 100% Accelerated Ageing
- Surge testing level option
- Improved basic reliability 0.5%/1000hrs
- Humidity 85°C/85%RH, Vr, 500/1000 hours
- - 55 to +125°C operation temperature
- Shock and Vibration by MIL-STD-202
- DCL 0.1 CV
- 3x reflow 260°C compatible
- Benign failure mode under recommended use conditions


### APPLICATIONS

Long life time DC/DC converter applications in Telecommunications, Industrial, Avionics.

For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)

### MARKING

#### B, D, Y CASE



### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|------------|----------------|------------------------------|------------------------------|------------------------------|------------------------------|--------------|
| B    | 1210     | 3528-21    | 3.50 (0.138)   | 2.80 (0.110)                 | 1.90 (0.075)                 | 2.20 (0.087)                 | 0.80 (0.031)                 | 1.40 (0.055) |
| D    | 2917     | 7343-31    | 7.30 (0.287)   | 4.30 (0.169)                 | 2.90 (0.114)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| Y    | 2917     | 7343-20    | 7.30 (0.287)   | 4.30 (0.169)                 | 2.00 (0.079) max             | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage |         |        |        |        |        |        |        |
|-------------|------|---------------|---------|--------|--------|--------|--------|--------|--------|
| µF          | Code | 4V(G)         | 6.3V(J) | 10V(A) | 16V(C) | 20V(D) | 25V(E) | 35V(V) | 50V(T) |
| 10          | 106  |               |         |        |        |        |        | D(70)  | D(120) |
| 15          | 156  |               |         |        |        |        | D(70)  |        |        |
| 22          | 226  |               | B(70)   |        |        | D(70)  |        |        |        |
| 33          | 336  |               | B(70)   |        | D(70)  |        |        |        |        |
| 47          | 476  |               | B(70)   |        | D(70)  |        |        |        |        |
| 68          | 686  |               |         | D(70)  |        |        |        |        |        |
| 100         | 107  |               |         | D(70)  |        |        |        |        |        |
| 150         | 157  |               | D(40)   |        |        |        |        |        |        |
| 220         | 227  | D(40), Y(40)  |         |        |        |        |        |        |        |

Available Ratings (ESR ratings in mOhms in brackets)  
Engineering samples – please contact manufacturer

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher voltage ratings in the same case size to the same reliability standards

# TCB Series



## COTS-Plus Polymer Capacitor

### HOW TO ORDER

#### AVX PART NUMBER:

| TCB  | D                                       | 107   | M                     | 010  | C                                 | □                                      | S  | Z                               | 0                              | ^  | 00   |
|------|---|---|-----------------------|--|-----------------------------------|--|--|---------------------------------|--------------------------------|--|--|
| Type | Case Size<br>See table on previous page | Capacitance Code<br>pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Tolerance<br>M = ±20% | Rated DC Voltage<br>004 = 4Vdc<br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | ESR<br>C = Std ESR<br>L = Low ESR | Packaging<br>R = 7" T&R<br>S = 13" T&R | Inspection Level<br>S = Standard Conformance | Reliability Grade<br>Z = Non-ER | Qualification Level<br>0 = N/A | Termination Finish<br>7 = 100% Tin<br>H* = Sn/Pb Non RoHS<br><br>*Contact Manufacturer | Surge Test Option<br>00 = Standard<br>23 = 10x Cycles, 25°C<br>24* = 10x Cycles, -55°C & +85°C<br><br>*Please contact AVX for Surge option |

### TECHNICAL SPECIFICATIONS

|                        |   |
|------------------------|---|
| Technical Data:        | All technical data relate to an ambient temperature of +25°C                      |
| Capacitance Range:     | 10µF to 220µF   |
| Capacitance Tolerance: | ±20%  |
| Leakage Current DCL:   | 0.1CV   |
| Temperature Range:     | -55°C to +125°C   |
| Basic Reliability:     | 0.5% per 1000 hours at 85°C, Vr with 0.1ΩV series impedance, 60% confidence level |
| Termination Finish:    | Sn Plating or SnPb Plating (Non RoHS)   |

NOTE: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges. Please reference the AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance.

# TCB Series



## COTS-Plus Polymer Capacitor

### RATINGS & PART NUMBER REFERENCE

| AVX Part No.        | Case Size | Capacitance (μF) | Rated Voltage (V) | Maximum Operating Temperature (°C) | DCL Max. (μA) | DF Max. (%) | ESR Max. @ 100kHz (mΩ) | MSL | 100kHz RMS Current (mA) |      |       |       | Humidity 85°C/85%RH, Vr (hrs) |  |
|---------------------|-----------|------------------|-------------------|------------------------------------|---------------|-------------|------------------------|-----|-------------------------|------|-------|-------|-------------------------------|--|
|                     |           |                  |                   |                                    |               |             |                        |     | 45°C                    | 85°C | 105°C | 125°C |                               |  |
| <b>4 Volt</b>       |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBD227M004C□SZ0700 | D         | 220              | 4                 | 125                                | 88            | 6           | 40                     | 3   | 2400                    | 1700 | 1100  | 600   | 1000                          |  |
| TCBD227M004C□SZ0723 | D         | 220              | 4                 | 125                                | 88            | 6           | 40                     | 3   | 2400                    | 1700 | 1100  | 600   | 1000                          |  |
| TCBY227M004C□SZ0700 | Y         | 220              | 4                 | 125                                | 88            | 6           | 40                     | 3   | 2200                    | 1500 | 1000  | 600   | 500                           |  |
| TCBY227M004C□SZ0723 | Y         | 220              | 4                 | 125                                | 88            | 6           | 40                     | 3   | 2200                    | 1500 | 1000  | 600   | 500                           |  |
| <b>6.3 Volt</b>     |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBB226M006C□SZ0700 | B         | 22               | 6.3               | 125                                | 13            | 6           | 70                     | 3   | 1300                    | 900  | 600   | 300   | 500                           |  |
| TCBB226M006C□SZ0723 | B         | 22               | 6.3               | 125                                | 13            | 6           | 70                     | 3   | 1300                    | 900  | 600   | 300   | 500                           |  |
| TCBB336M006C□SZ0700 | B         | 33               | 6.3               | 125                                | 19            | 6           | 70                     | 3   | 1300                    | 900  | 600   | 300   | 500                           |  |
| TCBB336M006C□SZ0723 | B         | 33               | 6.3               | 125                                | 19            | 6           | 70                     | 3   | 1300                    | 900  | 600   | 300   | 500                           |  |
| TCBB476M006C□SZ0700 | B         | 47               | 6.3               | 125                                | 28            | 6           | 70                     | 3   | 1300                    | 900  | 600   | 300   | 500                           |  |
| TCBB476M006C□SZ0723 | B         | 47               | 6.3               | 125                                | 28            | 6           | 70                     | 3   | 1300                    | 900  | 600   | 300   | 500                           |  |
| TCBD157M006C□SZ0700 | D         | 150              | 6.3               | 125                                | 90            | 6           | 40                     | 3   | 2400                    | 1700 | 1100  | 600   | 1000                          |  |
| TCBD157M006C□SZ0723 | D         | 150              | 6.3               | 125                                | 90            | 6           | 40                     | 3   | 2400                    | 1700 | 1100  | 600   | 1000                          |  |
| <b>10 Volt</b>      |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBD686M010C□SZ0700 | D         | 68               | 10                | 125                                | 68            | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD686M010C□SZ0723 | D         | 68               | 10                | 125                                | 68            | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD107M010C□SZ0700 | D         | 100              | 10                | 125                                | 100           | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD107M010C□SZ0723 | D         | 100              | 10                | 125                                | 100           | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| <b>16 Volt</b>      |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBD336M016C□SZ0700 | D         | 33               | 16                | 125                                | 52            | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD336M016C□SZ0723 | D         | 33               | 16                | 125                                | 52            | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD476M016C□SZ0700 | D         | 47               | 16                | 125                                | 75            | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD476M016C□SZ0723 | D         | 47               | 16                | 125                                | 75            | 6           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| <b>20 Volt</b>      |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBD226M020C□SZ0700 | D         | 22               | 20                | 125                                | 44            | 8           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD226M020C□SZ0723 | D         | 22               | 20                | 125                                | 44            | 8           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| <b>25 Volt</b>      |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBD156M025C□SZ0700 | D         | 15               | 25                | 125                                | 37            | 8           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD156M025C□SZ0723 | D         | 15               | 25                | 125                                | 37            | 8           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| <b>35 Volt</b>      |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBD106M035C□SZ0700 | D         | 10               | 35                | 125                                | 35            | 8           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| TCBD106M035C□SZ0723 | D         | 10               | 35                | 125                                | 35            | 8           | 70                     | 3   | 1800                    | 1300 | 800   | 500   | 1000                          |  |
| <b>50 Volt</b>      |           |                  |                   |                                    |               |             |                        |     |                         |      |       |       |                               |  |
| TCBD106M050C□SZ0700 | D         | 10               | 50                | 125                                | 50            | 10          | 120                    | 3   | 1400                    | 1000 | 600   | 400   | 500                           |  |
| TCBD106M050C□SZ0723 | D         | 10               | 50                | 125                                | 50            | 10          | 120                    | 3   | 1400                    | 1000 | 600   | 400   | 500                           |  |

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.



ESR allowed to move up to 1.25 times catalog limit post mounting.

**NOTE: AVX reserves the rights to supply higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

### RECOMMENDED DERATING FACTOR

Voltage and temperature derating as percentage of Vr.

| Rated voltage | Operating Temperature |       |       |
|---------------|-----------------------|-------|-------|
|               | ≤85°C                 | 105°C | 125°C |
| ≤10V          | 90%                   | 90%   | 60%   |
| ≥16V          | 80%                   | 80%   | 54%   |



# TCB Series



## COTS-Plus Polymer Capacitor


### QUALIFICATION TABLE

| TEST                              | TCB series (Temperature range -55°C to +125°C)  |               |               |                    |                                  |           |       |           |            |       |
|-----------------------------------|---|---------------|---------------|--------------------|----------------------------------|-----------|-------|-----------|------------|-------|
|                                   | Condition   |               |               | Characteristics    |                                  |           |       |           |            |       |
| <b>Endurance</b>                  | Determine after application of rated voltage for 2000 +48/-0 hours at 105±2°C. Also determine after application of 125°C temperature, 2/3 rated voltage for 2000 +48/-0 hours. After test leaving 1-2 hours at room temperature. Power supply impedance to be ≤ 0.1Ω/V. |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |   |               |               | DCL                | 1.25 x initial limit             |           |       |           |            |       |
|                                   |   |               |               | ΔC/C               | within +20/-30% of initial value |           |       |           |            |       |
|                                   |   |               |               | DF                 | 1.5 x initial limit              |           |       |           |            |       |
|                                   |   |               |               | ESR                | 2 x initial limit                |           |       |           |            |       |
| <b>Storage Life</b>               | 125°C, 0V, 2000h  |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |   |               |               | DCL                | 2 x initial limit                |           |       |           |            |       |
|                                   |   |               |               | ΔC/C               | within ±20% of initial value     |           |       |           |            |       |
|                                   |   |               |               | DF                 | 1.5 x initial limit              |           |       |           |            |       |
|                                   |   |               |               | ESR                | 2 x initial limit                |           |       |           |            |       |
| <b>Biased Humidity</b>            | Determine after leaving for 500 or 1000 hours at 85±2°C, 85% relative humidity and rated voltage and then recovery 1-2 hours at room temperature.   |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |   |               |               | DCL                | 3 x initial limit                |           |       |           |            |       |
|                                   |   |               |               | ΔC/C               | within +30/-20% of initial value |           |       |           |            |       |
|                                   |   |               |               | DF                 | 1.5 x initial limit              |           |       |           |            |       |
|                                   |   |               |               | ESR                | 2 x initial limit                |           |       |           |            |       |
| <b>Temperature Stability</b>      | Step  | Temperature°C | Duration(min) |                    | +20°C                            | -55°C     | +20°C | +85°C     | +125°C     | +20°C |
|                                   | 1   | +20±2         | 15            | DCL                | IL*                              | n/a       | IL*   | 10 x IL*  | 12.5 x IL* | IL*   |
|                                   | 2   | -55+0/-3      | 15            |                    |                                  |           |       |           |            |       |
|                                   | 3   | +20±2         | 15            | ΔC/C               | n/a                              | +0/-20%   | ±5%   | +20/-0%   | +30/-0%    | ±5%   |
|                                   | 4   | +85+3/-0      | 15            |                    |                                  |           |       |           |            |       |
|                                   | 5   | +125+3/-0     | 15            | DF                 | IL*                              | 1.5 x IL* | IL*   | 1.5 x IL* | 2 x IL*    | IL*   |
| 6                                 | +20±2   | 15            |               |                    |                                  |           |       |           |            |       |
| <b>Surge Voltage</b>              | <u>Test temperature: 125°C+3/0°C</u><br>Surge voltage: 1.3 x 2/3 rated voltage<br>Charge/Discharge resistance: 1000±100Ω<br>Number of cycles: 1000x<br>Cycle duration: 6min; 30sec charge, 5min 30sec discharge   |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |   |               |               | DCL                | initial limit                    |           |       |           |            |       |
|                                   |   |               |               | ΔC/C               | within +20/-30% of initial value |           |       |           |            |       |
|                                   |   |               |               | DF                 | 1.25 x initial limit             |           |       |           |            |       |
|                                   |   |               |               | ESR                | 1.25 x initial Limit             |           |       |           |            |       |
| <b>Mechanical Shock/Vibration</b> | MIL-STD-202, Method 213, Condition I, 100 G peak<br>MIL-STD-202, Method 204, Condition D, 10 Hz to 2,000 Hz, 20 G peak  |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |   |               |               | DCL                | initial limit                    |           |       |           |            |       |
|                                   |   |               |               | ΔC/C               | within ±10% of initial value     |           |       |           |            |       |
|                                   |   |               |               | DF                 | initial limit                    |           |       |           |            |       |
|                                   |   |               |               | ESR                | 1.25 x initial Limit             |           |       |           |            |       |

\*Initial Limit

For use outside of recommended conditions and special request, please contact manufacturer.  
 Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.

## COTS-Plus Polymer Solid Electrolytic Multianode Capacitor




### FEATURES

- Robust design for long operation lifetime
- Volumetric efficiency
- AVX Q-process with statistical screening
- 100% Accelerated Ageing
- Surge testing level option
- Improved basic reliability 0.5%/1000hrs
- Humidity 85°C/85%RH, Vr, 500 hours
- -55 to +125°C operation temperature
- Shock and Vibration by MIL-STD-202
- DCL 0.1 CV
- Low ESR
- 3x reflow 260°C compatible
- High frequency capacitance retention
- Benign failure mode under recommended use conditions




For RoHS compliant products, please select correct termination style.



### MARKING

#### E CASE



### APPLICATIONS

- Long life time DC/DC converter applications in Telecommunications, Industrial, Avionics.

For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)

### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | EIA Metric | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W,±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|------------|----------------|------------------------------|------------------------------|-----------------|------------------------------|--------------|
| E    | 2917     | 7343-43    | 7.30 (0.287)   | 4.30 (0.169)                 | 4.10 (0.162)                 | 2.40 (0.094)    | 1.30 (0.051)                 | 4.40 (0.173) |

W1 dimension applies to the termination width for A dimensional area only.

### HOW TO ORDER

| TCS  | E               | 477  | M         | 006  | C                          | □                         | S                        | Z                 | 0                   | ^                                     | ++  |
|------|-----------------|--|-----------|--|----------------------------|---------------------------|--------------------------|-------------------|---------------------|---------------------------------------|---|
| Type | Case Size       | Capacitance Code   | Tolerance | Rated DC Voltage                           | ESR                        | Packaging                 | Inspection Level         | Reliability Grade | Qualification Level | Termination Finish                    | Surge Test Option   |
|      | See table above | pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow) | M = ±20%  | 002 = 2.5Vdc<br>004 = 4Vdc<br>006 = 6.3Vdc | C = Std ESR<br>L = Low ESR | R = 7" T&R<br>S = 13" T&R | S = Standard Conformance | Z = Non-ER        | 0 = N/A             | 7 = 100% Tin<br>H = Sn/Pb<br>Non RoHS | 00 = Standard<br>23 = 10x Cycles, 25°C<br>24* = 10x Cycles, -55°C & +85°C |

\*Please contact AVX for Surge option

### TECHNICAL SPECIFICATIONS

|                        |  |
|------------------------|--|
| Technical Data:        | All technical data relate to an ambient temperature of +25°C                       |
| Capacitance Range:     | 330 µF to 1000 µF  |
| Capacitance Tolerance: | ±20%   |
| Leakage Current DCL:   | 0.1CV  |
| Temperature Range:     | -55°C to +125°C  |
| Reliability:           | 0.5% per 1000 hours at 85°C, Vr with 0.1Ω/V series impedance, 60% confidence level |
| Termination Finish:    | Sn Plating or SnPb Plating (Non RoHS)  |

NOTE: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges. Please reference the AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance.

### CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) |          |          |
|-------------|------|------------------------------------|----------|----------|
| μF          | Code | 2.5 (e)                            | 4V (G)   | 6.3V (J) |
| 330         | 337  |                                    |          | E(15)    |
| 470         | 477  | E(10,12)                           | E(10,12) | E(10,12) |
| 680         | 687  | E(10,12)                           | E(10,12) |          |
| 1000        | 108  | E(10,12)                           | E(10,12) |          |

Available Ratings, (ESR ratings in mOhms in brackets)

Engineering samples – please contact manufacturer

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards.

### RATINGS & PART NUMBER REFERENCE

| AVX Part No.        | Case Size | Capacitance (μF) | Rated Voltage (V) | Maximum Operating Temperature (°C) | DCL Max. (μA) | DF Max. (%) | ESR Max @ 100kHz (mΩ) | 100kHz RMS Current (mA) |      |       |       | MSL |
|---------------------|-----------|------------------|-------------------|------------------------------------|---------------|-------------|-----------------------|-------------------------|------|-------|-------|-----|
|                     |           |                  |                   |                                    |               |             |                       | 45°C                    | 85°C | 105°C | 125°C |     |
| <b>2.5 Volt</b>     |           |                  |                   |                                    |               |             |                       |                         |      |       |       |     |
| TCSE477M002L□SZ0^++ | E         | 470              | 2.5               | 125                                | 117.5         | 8           | 10                    | 6400                    | 4500 | 2900  | 1600  | 3   |
| TCSE477M002C□SZ0^++ | E         | 470              | 2.5               | 125                                | 117.5         | 8           | 12                    | 5800                    | 4100 | 2600  | 1500  | 3   |
| TCSE687M002L□SZ0^++ | E         | 680              | 2.5               | 125                                | 170           | 8           | 10                    | 6400                    | 4500 | 2900  | 1600  | 3   |
| TCSE687M002C□SZ0^++ | E         | 680              | 2.5               | 125                                | 170           | 8           | 12                    | 5800                    | 4100 | 2600  | 1500  | 3   |
| TCSE108M002L□SZ0^++ | E         | 1000             | 2.5               | 125                                | 250           | 8           | 10                    | 6400                    | 4500 | 2900  | 1600  | 3   |
| TCSE108M002C□SZ0^++ | E         | 1000             | 2.5               | 125                                | 250           | 8           | 12                    | 5800                    | 4100 | 2600  | 1500  | 3   |
| <b>4 Volt</b>       |           |                  |                   |                                    |               |             |                       |                         |      |       |       |     |
| TCSE477M004L□SZ0^++ | E         | 470              | 4                 | 125                                | 188           | 8           | 10                    | 6400                    | 4500 | 2900  | 1600  | 3   |
| TCSE477M004C□SZ0^++ | E         | 470              | 4                 | 125                                | 188           | 8           | 12                    | 5800                    | 4100 | 2600  | 1500  | 3   |
| TCSE687M004L□SZ0^++ | E         | 680              | 4                 | 125                                | 272           | 8           | 10                    | 6400                    | 4500 | 2900  | 1600  | 3   |
| TCSE687M004C□SZ0^++ | E         | 680              | 4                 | 125                                | 272           | 8           | 12                    | 5800                    | 4100 | 2600  | 1500  | 3   |
| TCSE108M004L□SZ0^++ | E         | 1000             | 4                 | 125                                | 400           | 8           | 10                    | 6400                    | 4500 | 2900  | 1600  | 3   |
| TCSE108M004C□SZ0^++ | E         | 1000             | 4                 | 125                                | 400           | 8           | 12                    | 5800                    | 4100 | 2600  | 1500  | 3   |
| <b>6.3 Volt</b>     |           |                  |                   |                                    |               |             |                       |                         |      |       |       |     |
| TCSE337M006C□SZ0^++ | E         | 330              | 6.3               | 125                                | 208           | 8           | 15                    | 5200                    | 3600 | 2300  | 1300  | 3   |
| TCSE477M006L□SZ0^++ | E         | 470              | 6.3               | 125                                | 296           | 8           | 10                    | 6400                    | 4500 | 2900  | 1600  | 3   |
| TCSE477M006C□SZ0^++ | E         | 470              | 6.3               | 125                                | 296           | 8           | 12                    | 5800                    | 4100 | 2600  | 1500  | 3   |

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.



ESR allowed to move up to 1.25 times catalog limit post mounting.

**NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.**

### RECOMMENDED DERATING FACTOR

Voltage and temperature derating as percentage of V<sub>R</sub>.

| Rated voltage | Operating Temperature |       |       |
|---------------|-----------------------|-------|-------|
|               | ≤85°C                 | 105°C | 125°C |
| ≤10V          | 90%                   | 90%   | 60%   |
| ≥16V          | 80%                   | 80%   | 54%   |




### QUALIFICATION TABLE

| TEST                              | TCS COST-Plus series (Temperature range -55°C to +125°C)   |               |               |                    |                                  |           |       |           |            |       |
|-----------------------------------|--|---------------|---------------|--------------------|----------------------------------|-----------|-------|-----------|------------|-------|
|                                   | Condition  |               |               | Characteristics    |                                  |           |       |           |            |       |
| <b>Endurance</b>                  | Determine after application of rated voltage for 2000 +48/-0 hours at 105±2°C. Also determine after application of 125°C temperature, 2/3 rated voltage for 2000 +48/-0 hours. After test leaving 1-2 hours at room temperature. Power supply impedance to be ≤0.1Ω/V. |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |  |               |               | DCL                | 1.25 x initial limit             |           |       |           |            |       |
|                                   |  |               |               | ΔC/C               | within +20/-30% of initial value |           |       |           |            |       |
|                                   |  |               |               | DF                 | 1.5 x initial limit              |           |       |           |            |       |
|                                   |  |               |               | ESR                | 2 x initial limit                |           |       |           |            |       |
| <b>Storage Life</b>               | 125°C, 0V, 2000h   |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |  |               |               | DCL                | 2 x initial limit                |           |       |           |            |       |
|                                   |  |               |               | ΔC/C               | within ±20% of initial value     |           |       |           |            |       |
|                                   |  |               |               | DF                 | 1.5 x initial limit              |           |       |           |            |       |
|                                   |  |               |               | ESR                | 2 x initial limit                |           |       |           |            |       |
| <b>Biased Humidity</b>            | Determine after leaving for 500 or 1000 hours at 85±2°C, 85% relative humidity and rated voltage and then recovery 1-2 hours at room temperature.  |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |  |               |               | DCL                | 3 x initial limit                |           |       |           |            |       |
|                                   |  |               |               | ΔC/C               | within +30/-20% of initial value |           |       |           |            |       |
|                                   |  |               |               | DF                 | 1.5 x initial limit              |           |       |           |            |       |
|                                   |  |               |               | ESR                | 2 x initial limit                |           |       |           |            |       |
| <b>Temperature Stability</b>      | Step   | Temperature°C | Duration(min) |                    | +20°C                            | -55°C     | +20°C | +85°C     | +125°C     | +20°C |
|                                   | 1  | +20±2         | 15            |                    |                                  |           |       |           |            |       |
|                                   | 2  | -55+0/-3      | 15            | DCL                | IL*                              | n/a       | IL*   | 10 x IL*  | 12.5 x IL* | IL*   |
|                                   | 3  | +20±2         | 15            |                    |                                  |           |       |           |            |       |
|                                   | 4  | +85+3/-0      | 15            | ΔC/C               | n/a                              | +0/-20%   | ±5%   | +20/-0%   | +30/-0%    | ±5%   |
|                                   | 5  | +125+3/-0     | 15            |                    |                                  |           |       |           |            |       |
|                                   | 6  | +20±2         | 15            | DF                 | IL*                              | 1.5 x IL* | IL*   | 1.5 x IL* | 2 x IL*    | IL*   |
| <b>Surge Voltage</b>              | Test temperature: 125°C+3/0°C<br>Surge voltage: 1.3 x 2/3 rated voltage<br>Charge/Discharge resistance: 1000±100Ω<br>Number of cycles: 1000x<br>Cycle duration: 6 min; 30 sec charge,<br>5 min 30 sec discharge  |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |  |               |               | DCL                | initial limit                    |           |       |           |            |       |
|                                   |  |               |               | ΔC/C               | within +20/-30% of initial value |           |       |           |            |       |
|                                   |  |               |               | DF                 | 1.25 x initial limit             |           |       |           |            |       |
|                                   |  |               |               | ESR                | 1.25 x initial limit             |           |       |           |            |       |
| <b>Mechanical Shock/Vibration</b> | MIL-STD-202, Method 213, Condition I, 100 G peak<br>MIL-STD-202, Method 204, Condition D, 10 Hz to 2,000 Hz, 20 G peak   |               |               | Visual examination | no visible damage                |           |       |           |            |       |
|                                   |  |               |               | DCL                | initial limit                    |           |       |           |            |       |
|                                   |  |               |               | ΔC/C               | within ±10% of initial value     |           |       |           |            |       |
|                                   |  |               |               | DF                 | initial limit                    |           |       |           |            |       |
|                                   |  |               |               | ESR                | 1.25 x initial limit             |           |       |           |            |       |

\*Initial Limit

For use outside of recommended conditions and special request, please contact manufacturer.  
Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.


## Wet Electrolytic Tantalum Capacitor



The DSCC 93026 series is an axial leaded wet electrolytic tantalum capacitor and represents a new level of high CV (capacitance/voltage) previously unavailable in this technology. These components incorporate a novel, very high capacitance cathode system that allows for higher CV designs, well beyond values specified in the MIL-PRF-39006 drawing.

This design includes a welded tantalum can and header assembly that provides a hermetic seal to withstand harsh shock and vibration requirements of 39006. Wet tantalums do not require the same derating as solid tantalums. AVX recommends derating components by only 20% in order to enhance reliability.

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)

| DSCC Case Size | AVX Case Size | L                              | D                         |                        | E             |
|----------------|---------------|--------------------------------|---------------------------|------------------------|---------------|
|                |               |                                | Without Insulating Sleeve | With Insulating Sleeve |               |
|                |               | +0.79 (0.031)<br>-0.41 (0.016) | ±0.41 (0.016)             | Max                    | ±6.35 (0.250) |
| T1             | A             | 11.51 (0.453)                  | 4.78 (0.188)              | 5.56 (0.219)           | 38.10 (1.500) |
| T2             | B             | 16.28 (0.641)                  | 7.14 (0.281)              | 7.92 (0.312)           | 57.15 (2.250) |
| T3             | D             | 19.46 (0.766)                  | 9.52 (0.375)              | 10.31 (0.406)          | 57.15 (2.250) |
| T4             | E             | 26.97 (1.062)                  | 9.52 (0.375)              | 10.31 (0.406)          | 57.15 (2.250) |


### VOLTAGE RATINGS (Operating Temperature -55°C to 125°C)

| Voltage (DC)          |       |      |      |      |    |      |     |     |
|-----------------------|-------|------|------|------|----|------|-----|-----|
| Rated Voltage: (Ur)   | 85°C  | 25   | 30   | 50   | 60 | 75   | 100 | 125 |
| Derated Voltage: (Uc) | 125°C | 15   | 20   | 30   | 40 | 50   | 65  | 85  |
| Surge Voltage: (Us)   | 85°C  | 28.8 | 34.5 | 57.5 | 69 | 86.3 | 115 | 144 |



## Wet Electrolytic Tantalum Capacitor

### HOW TO ORDER DSCC 93026 PART NUMBER:



Not RoHS Compliant

### RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/</sup>

| Frequency of Applied Ripple Current |         | 120Hz |      |      |      | 800Hz |      |      |      | 1kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |
| Ambient Still Air Temperature (°C)  | 100%    | 0.60  | 0.39 | –    | –    | 0.71  | 0.43 | –    | –    | 0.72 | 0.45 | –    | –    |
|                                     | 85°C    | 0.60  | 0.46 | –    | –    | 0.71  | 0.55 | –    | –    | 0.72 | 0.55 | –    | –    |
| Rated Peak                          | 80%     | 0.60  | 0.52 | 0.35 | –    | 0.71  | 0.62 | 0.42 | –    | 0.72 | 0.62 | 0.42 | –    |
|                                     | 70%     | 0.60  | 0.58 | 0.44 | –    | 0.71  | 0.69 | 0.52 | –    | 0.72 | 0.70 | 0.52 | –    |
| Voltage                             | 66-2/3% | 0.60  | 0.60 | 0.46 | 0.27 | 0.71  | 0.71 | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |

| Frequency of Applied Ripple Current |         | 10kHz |      |      |      | 40kHz |      |      |      | 100kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|--------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |
| % of                                | 100%    | 0.88  | 0.55 | –    | –    | 1.00  | 0.63 | –    | –    | 1.10   | 0.69 | –    | –    |
|                                     | 85°C    | 0.88  | 0.67 | –    | –    | 1.00  | 0.77 | –    | –    | 1.10   | 0.85 | –    | –    |
| Rated Peak                          | 80%     | 0.88  | 0.76 | 0.52 | –    | 1.00  | 0.87 | 0.59 | –    | 1.10   | 0.96 | 0.65 | –    |
|                                     | 70%     | 0.88  | 0.85 | 0.64 | –    | 1.00  | 0.97 | 0.73 | –    | 1.10   | 1.07 | 0.80 | –    |
| Voltage                             | 66-2/3% | 0.88  | 0.88 | 0.68 | 0.40 | 1.00  | 1.00 | 0.77 | 0.45 | 1.10   | 1.10 | 0.85 | 0.50 |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.

# DSCC 93026



## Wet Electrolytic Tantalum Capacitor

### RATINGS & PART NUMBER REFERENCE

| DSCC Part Number                       | Cap (µF)<br>25°C<br>at 120Hz | DC Rated Voltage (V)<br>at 85°C | ESR max (ohms)<br>at 120Hz | DC Leakage max (µA) |                | Impedance max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms)<br>85°C at 40kHz | Case Size |      |
|--|------------------------------|---------------------------------|----------------------------|---------------------|----------------|--|--------------------------------|-------|--------|-------------------------------------|-----------|------|
|  |                              |                                 |                            | +25°C               | +85°C & +125°C |  | -55°C                          | +85°C | +125°C |                                     | AVX       | DSCC |
| <b>25 VDC at 85°C 15 VDC at 125°C</b>  |                              |                                 |                            |                     |                |  |                                |       |        |                                     |           |      |
| 93026-29*□                             | 120                          | 25                              | 1.3                        | 1                   | 5              | 25                                     | -42                            | 8     | 12     | 1250                                | A         | T1   |
| 93026-30*□                             | 560                          | 25                              | 0.83                       | 2                   | 10             | 12                                     | -65                            | 10    | 15     | 2100                                | B         | T2   |
| 93026-31*□                             | 1200                         | 25                              | 0.65                       | 5                   | 20             | 7                                      | -70                            | 12    | 18     | 2600                                | D         | T3   |
| 93026-32*□                             | 1800                         | 25                              | 0.5                        | 6                   | 25             | 7                                      | -75                            | 12    | 20     | 3100                                | E         | T4   |
| 93026-64*□                             | 2200                         | 25                              | 0.5                        | 10                  | 80             | 10                                     | -90                            | 30    | 50     | 3200                                | E         | T4   |
| <b>30 VDC at 85°C 20 VDC at 125°C</b>  |                              |                                 |                            |                     |                |  |                                |       |        |                                     |           |      |
| 93026-33*□                             | 100                          | 30                              | 1.3                        | 1                   | 5              | 25                                     | -38                            | 8     | 12     | 1200                                | A         | T1   |
| 93026-34*□                             | 470                          | 30                              | 0.85                       | 2                   | 10             | 15                                     | -65                            | 10    | 18     | 1800                                | B         | T2   |
| 93026-35*□                             | 1000                         | 30                              | 0.7                        | 7                   | 25             | 7                                      | -70                            | 10    | 18     | 2500                                | D         | T3   |
| 93026-36*□                             | 1500                         | 30                              | 0.6                        | 12                  | 35             | 6                                      | -72                            | 10    | 20     | 3000                                | E         | T4   |
| <b>50 VDC at 85°C 30 VDC at 125°C</b>  |                              |                                 |                            |                     |                |  |                                |       |        |                                     |           |      |
| 93026-37*□                             | 68                           | 50                              | 1.5                        | 1                   | 5              | 35                                     | -25                            | 8     | 15     | 1050                                | A         | T1   |
| 93026-38*□                             | 220                          | 50                              | 0.9                        | 2                   | 10             | 17.5                                   | -50                            | 8     | 15     | 1800                                | B         | T2   |
| 93026-39*□                             | 470                          | 50                              | 0.75                       | 3                   | 25             | 10                                     | -50                            | 8     | 15     | 2100                                | D         | T3   |
| 93026-40*□                             | 680                          | 50                              | 0.7                        | 5                   | 40             | 8                                      | -58                            | 10    | 20     | 2750                                | E         | T4   |
| <b>60 VDC at 85°C 40 VDC at 125°C</b>  |                              |                                 |                            |                     |                |  |                                |       |        |                                     |           |      |
| 93026-41*□                             | 47                           | 60                              | 2                          | 1                   | 5              | 44                                     | -25                            | 8     | 12     | 1050                                | A         | T1   |
| 93026-42*□                             | 150                          | 60                              | 1.1                        | 2                   | 10             | 20                                     | -40                            | 8     | 15     | 1650                                | B         | T2   |
| 93026-43*□                             | 390                          | 60                              | 0.9                        | 3                   | 25             | 15                                     | -60                            | 8     | 15     | 2100                                | D         | T3   |
| 93026-44*□                             | 560                          | 60                              | 0.8                        | 5                   | 40             | 10                                     | -58                            | 8     | 15     | 2750                                | E         | T4   |
| 93026-65*□                             | 1000                         | 60                              | 1                          | 12                  | 90             | 20                                     | -90                            | 30    | 50     | 3200                                | E         | T4   |
| <b>75 VDC at 85°C 50 VDC at 125°C</b>  |                              |                                 |                            |                     |                |  |                                |       |        |                                     |           |      |
| 93026-45*□                             | 33                           | 75                              | 2.5                        | 1                   | 5              | 66                                     | -25                            | 5     | 9      | 1050                                | A         | T1   |
| 93026-46*□                             | 110                          | 75                              | 1.3                        | 2                   | 10             | 24                                     | -35                            | 6     | 10     | 1650                                | B         | T2   |
| 93026-47*□                             | 330                          | 75                              | 1                          | 3                   | 30             | 12                                     | -45                            | 6     | 10     | 2100                                | D         | T3   |
| 93026-48*□                             | 470                          | 75                              | 0.9                        | 5                   | 50             | 12                                     | -55                            | 6     | 10     | 2750                                | E         | T4   |
| <b>100 VDC at 85°C 65 VDC at 125°C</b> |                              |                                 |                            |                     |                |  |                                |       |        |                                     |           |      |
| 93026-49*□                             | 15                           | 100                             | 3.5                        | 1                   | 5              | 125                                    | -18                            | 3     | 10     | 1050                                | A         | T1   |
| 93026-50*□                             | 68                           | 100                             | 2.1                        | 2                   | 10             | 37                                     | -30                            | 4     | 12     | 1650                                | B         | T2   |
| 93026-51*□                             | 150                          | 100                             | 1.6                        | 3                   | 25             | 22                                     | -35                            | 6     | 12     | 2100                                | D         | T3   |
| 93026-52*□                             | 220                          | 100                             | 1.2                        | 5                   | 50             | 15                                     | -40                            | 6     | 12     | 2750                                | E         | T4   |
| <b>125 VDC at 85°C 85 VDC at 125°C</b> |                              |                                 |                            |                     |                |  |                                |       |        |                                     |           |      |
| +93026-53*□                            | 10                           | 125                             | 5.5                        | 1                   | 5              | 175                                    | -15                            | 3     | 10     | 1050                                | A         | T1   |
| +93026-54*□                            | 47                           | 125                             | 2.3                        | 2                   | 10             | 47                                     | -25                            | 5     | 12     | 1650                                | B         | T2   |
| 93026-55*□                             | 100                          | 125                             | 1.8                        | 3                   | 25             | 35                                     | -35                            | 5     | 12     | 2100                                | D         | T3   |
| 93026-56*□                             | 150                          | 125                             | 1.6                        | 5                   | 50             | 20                                     | -35                            | 6     | 12     | 2750                                | E         | T4   |

+ Contact factory of leadtime and availability

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

## COTS-Plus Wet Electrolytic Tantalum Capacitor




The TWA series is an axial leaded wet electrolytic tantalum capacitor with a unique cathode system that promotes very high CV (Capacitance/Voltage) per cc in traditional MIL-PRF-39006 case sizes.

The series also utilizes a welded tantalum can and header assembly to provide a hermetic seal and subsequent long operating lifetime.

The construction is similar to DSCC 93026 with capability of meeting harsh shock and vibration conditions.

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)

| DSCC Case Size | AVX Case Size | L<br>+0.79 (0.031)<br>-0.41 (0.016) | D  |                               | E<br>±6.35 (0.250) |
|----------------|---------------|-------------------------------------|--|-------------------------------|--------------------|
|                |               |                                     | Without Insulating Sleeve<br>±0.41 (0.016) | With Insulating Sleeve<br>Max |                    |
| T1             | A             | 11.51 (0.453)                       | 4.78 (0.188)                               | 5.56 (0.219)                  | 38.10 (1.500)      |
| T2             | B             | 16.28 (0.641)                       | 7.14 (0.281)                               | 7.92 (0.312)                  | 57.15 (2.250)      |
| T3             | D             | 19.46 (0.766)                       | 9.52 (0.375)                               | 10.31 (0.406)                 | 57.15 (2.250)      |
| T4             | E             | 26.97 (1.062)                       | 9.52 (0.375)                               | 10.31 (0.406)                 | 57.15 (2.250)      |

### VOLTAGE RATINGS (Operating Temperature -55°C to 125°C)

| Voltage (DC)                       |       |      |      |      |      |    |      |     |     |
|------------------------------------|-------|------|------|------|------|----|------|-----|-----|
| Rated Voltage: (V <sub>R</sub> )   | 85°C  | 15   | 25   | 30   | 50   | 60 | 75   | 100 | 125 |
| Derated Voltage: (V <sub>C</sub> ) | 125°C | 10   | 15   | 20   | 30   | 40 | 50   | 65  | 85  |
| Surge Voltage: (V <sub>S</sub> )   | 85°C  | 17.3 | 28.8 | 34.5 | 57.5 | 69 | 86.3 | 115 | 144 |


# TWA Series



## COTS-Plus Wet Electrolytic Tantalum Capacitor

### HOW TO ORDER

#### AVX PART NUMBER:



\* Please contact the factory for additional details and availability.



### RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/</sup>

| Frequency of Applied Ripple Current |      | 120Hz |      |      |      | 800Hz |      |      |      | 1kHz |      |      |     |
|-------------------------------------|------|-------|------|------|------|-------|------|------|------|------|------|------|-----|
|                                     |      | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125 |
| % of 85°C Rated Peak Voltage        | 100% | 0.60  | 0.39 | –    | –    | 0.71  | 0.43 | –    | –    | 0.72 | 0.45 | –    | –   |
|                                     | 90%  | 0.60  | 0.46 | –    | –    | 0.71  | 0.55 | –    | –    | 0.72 | 0.55 | –    | –   |
| 80%                                 | 80%  | 0.60  | 0.52 | 0.35 | –    | 0.71  | 0.62 | 0.42 | –    | 0.72 | 0.62 | 0.42 | –   |
|                                     | 70%  | 0.60  | 0.58 | 0.44 | –    | 0.71  | 0.69 | 0.52 | –    | 0.72 | 0.70 | 0.52 | –   |
| 66-2/3%                             | 0.60 | 0.60  | 0.46 | 0.27 | 0.71 | 0.71  | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |     |

| Frequency of Applied Ripple Current |      | 10kHz |      |      |      | 40kHz |      |      |      | 100kHz |      |      |     |
|-------------------------------------|------|-------|------|------|------|-------|------|------|------|--------|------|------|-----|
|                                     |      | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125 |
| % of 85°C Rated Peak Voltage        | 100% | 0.88  | 0.55 | –    | –    | 1.00  | 0.63 | –    | –    | 1.10   | 0.69 | –    | –   |
|                                     | 90%  | 0.88  | 0.67 | –    | –    | 1.00  | 0.77 | –    | –    | 1.10   | 0.85 | –    | –   |
| 80%                                 | 80%  | 0.88  | 0.76 | 0.52 | –    | 1.00  | 0.87 | 0.59 | –    | 1.10   | 0.96 | 0.65 | –   |
|                                     | 70%  | 0.88  | 0.85 | 0.64 | –    | 1.00  | 0.97 | 0.73 | –    | 1.10   | 1.07 | 0.80 | –   |
| 66-2/3%                             | 0.88 | 0.88  | 0.68 | 0.40 | 1.00 | 1.00  | 0.77 | 0.45 | 1.10 | 1.10   | 0.85 | 0.50 |     |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.

## COTS-Plus Wet Electrolytic Tantalum Capacitor

### CAPACITANCE AND RATED VOLTAGE, $V_R$ (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance   |      | Rated Voltage DC ( $V_R$ ) to 85°C |     |     |                  |                  |                  |                  |      |
|---------------|------|------------------------------------|-----|-----|------------------|------------------|------------------|------------------|------|
| $\mu\text{F}$ | Code | 15V                                | 25V | 30V | 50V              | 60V              | 75V              | 100V             | 125V |
| 10            | 106  |                                    |     |     |                  |                  |                  | A <sup>(M)</sup> | A    |
| 15            | 156  |                                    |     |     |                  |                  |                  | A                |      |
| 22            | 226  |                                    |     |     |                  |                  |                  | B                |      |
| 27            | 276  |                                    |     |     |                  |                  |                  |                  | B    |
| 33            | 336  |                                    |     |     |                  |                  | A                |                  |      |
| 47            | 476  |                                    |     |     | B                | A                |                  |                  | B    |
| 68            | 686  |                                    | A   |     | A                |                  | A <sup>(M)</sup> | B                |      |
| 82            | 826  |                                    |     |     |                  |                  |                  |                  | E    |
| 100           | 107  |                                    |     | A   | A <sup>(M)</sup> | B                | B                |                  | D    |
| 110           | 117  |                                    |     |     |                  |                  | B                |                  |      |
| 120           | 127  |                                    | A   |     | B                |                  |                  |                  | D    |
| 150           | 157  |                                    |     |     | B                | B                |                  | D                | E    |
| 220           | 227  |                                    |     | B   | B                |                  | E                | D,E              | E    |
| 270           | 277  |                                    | B   |     |                  |                  |                  |                  |      |
| 330           | 337  |                                    | B   |     | E                |                  | D,E              | E                |      |
| 390           | 397  | D                                  |     |     |                  | D                |                  |                  |      |
| 400           | 407  |                                    |     |     |                  |                  |                  | E                |      |
| 470           | 477  |                                    |     | B   | D,E              |                  | E                | E                |      |
| 560           | 567  |                                    | B   |     |                  | E                |                  | E                |      |
| 660           | 667  |                                    |     |     |                  |                  | E                |                  |      |
| 680           | 687  |                                    | E   | D,E | E                | E                | E                |                  |      |
| 750           | 757  |                                    | D,E | D,E | E                | E                | E                | E                |      |
| 1000          | 108  |                                    | D,E | D,E | D,E              | E                | E                |                  |      |
| 1200          | 128  |                                    | D   |     | E                |                  |                  |                  |      |
| 1500          | 158  |                                    | E   | E   | E                |                  |                  |                  |      |
| 1800          | 188  |                                    | E   |     |                  |                  |                  |                  |      |
| 2200          | 228  |                                    | E   |     |                  | E <sup>(M)</sup> |                  |                  |      |
| 3000          | 308  |                                    |     |     | E <sup>(M)</sup> |                  |                  |                  |      |
| 4700          | 478  |                                    | E   |     |                  |                  |                  |                  |      |

Available Ratings <sup>(M tolerance only)</sup>

Engineering samples - please contact manufacturer

# TWA Series



## COTS-Plus Wet Electrolytic Tantalum Capacitor

### RATINGS & PART NUMBER REFERENCE

| AVX Part Number                       | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | ESR Max<br>(Ohms)<br>at 120Hz | DC Leakage max (µA) |                 | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance Change<br>(%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |      |
|---------------------------------------|------------------------------|------------------------------------|-------------------------------|---------------------|-----------------|---|-----------------------------------|-------|--------|--|-----------|------|
|                                       |                              |                                    |                               | +25°C               | +85 &<br>+125°C |   | -55°C                             | +85°C | +125°C |  | AVX       | DSCC |
| <b>15 VDC at 85°C 10 VDC at 125°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAD397*015□BSZ0^00                   | 390                          | 15                                 | 1.7                           | 7                   | 28              | 48  | -70                               | 25    | 25     | 1396                                   | D         | T3   |
| <b>25 VDC at 85°C 15 VDC at 125°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAA686*025□BEZ0^00                   | 68                           | 25                                 | 2.5                           | 0.6                 | 3               | 45  | -40                               | 12    | 15     | 850                                    | A         | T1   |
| TWAA127*025□BSZ0000                   | 120                          | 25                                 | 1.3                           | 1                   | 5               | 25  | -42                               | 8     | 12     | 1250                                   | A         | T1   |
| TWAA127*025□BEZ0^00*                  | 120                          | 25                                 | 2.3                           | 2                   | 10              | 35  | -42                               | 20    | 25     | 1250                                   | A         | T1   |
| TWAB277*025□BEZ0^00                   | 270                          | 25                                 | 0.9                           | 4                   | 20              | 17.5                                      | -50                               | 18    | 28     | 1800                                   | B         | T2   |
| TWAB337*025□BEZ0^00                   | 330                          | 25                                 | 1.3                           | 2                   | 20              | 25  | -60                               | 10    | 15     | 1550                                   | B         | T2   |
| TWAB567*025□BSZ0^00                   | 560                          | 25                                 | 0.83                          | 2                   | 10              | 12  | -65                               | 10    | 15     | 2100                                   | B         | T2   |
| TWAE687*025□BEZ0^00                   | 680                          | 25                                 | 0.75                          | 3                   | 12              | 12  | -50                               | 8     | 15     | 2100                                   | E         | T4   |
| TWAD757*025□BEZ0^00                   | 750                          | 25                                 | 1                             | 3                   | 25              | 15  | -50                               | 8     | 15     | 2000                                   | D         | T3   |
| TWAE757*025□BEZ0^00                   | 750                          | 25                                 | 0.75                          | 3.5                 | 16              | 9   | -55                               | 10    | 18     | 2200                                   | E         | T4   |
| TWAD108*025□BEZ0^00                   | 1000                         | 25                                 | 1                             | 4                   | 30              | 15  | -50                               | 8     | 15     | 2300                                   | D         | T3   |
| TWAE108*025□BEZ0^00                   | 1000                         | 25                                 | 0.7                           | 4                   | 20              | 9   | -55                               | 10    | 18     | 2400                                   | E         | T4   |
| TWAD128*025□BSZ0^00                   | 1200                         | 25                                 | 0.65                          | 5                   | 20              | 7   | -70                               | 12    | 18     | 2600                                   | D         | T3   |
| TWAD128*025□BEZ0^00*                  | 1200                         | 25                                 | 0.65                          | 5                   | 20              | 7   | -70                               | 12    | 18     | 2600                                   | D         | T3   |
| TWAE158*025□BSZ0^00                   | 1500                         | 25                                 | 0.5                           | 6                   | 24              | 7   | -65                               | 15    | 20     | 2850                                   | E         | T4   |
| TWAE188*025□BSZ0^00                   | 1800                         | 25                                 | 0.5                           | 6                   | 25              | 7   | -75                               | 12    | 20     | 3100                                   | E         | T4   |
| TWAE228*025□BSZ0^00                   | 2200                         | 25                                 | 0.5                           | 10                  | 80              | 10  | -90                               | 30    | 50     | 3200                                   | E         | T4   |
| TWAE478*025□BSZ0^00                   | 4700                         | 25                                 | 0.5                           | 30                  | 180             | 5   | -90                               | 60    | 80     | 4250                                   | E         | T4   |
| TWAE478*025□BEZ0^00*                  | 4700                         | 25                                 | 0.5                           | 30                  | 180             | 5   | -90                               | 60    | 80     | 4250                                   | E         | T4   |
| <b>30 VDC at 85°C 20 VDC at 125°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAA107*030□BSZ0000                   | 100                          | 30                                 | 1.3                           | 1                   | 5               | 25  | -38                               | 8     | 12     | 1200                                   | A         | T1   |
| TWAA107*030□BEZ0^00*                  | 100                          | 30                                 | 2.3                           | 2                   | 10              | 35  | -38                               | 20    | 25     | 1200                                   | A         | T1   |
| TWAB227*030□BEZ0^00                   | 220                          | 30                                 | 2                             | 1.9                 | 10              | 40  | -40                               | 18    | 28     | 1200                                   | B         | T2   |
| TWAB477*030□BSZ0^00                   | 470                          | 30                                 | 0.85                          | 2                   | 10              | 15  | -65                               | 10    | 18     | 1800                                   | B         | T2   |
| TWAD687*030□BEZ0^00                   | 680                          | 30                                 | 1                             | 3.3                 | 25              | 15  | -50                               | 8     | 15     | 1900                                   | D         | T3   |
| TWAE687*030□BEZ0^00                   | 680                          | 30                                 | 0.8                           | 4.5                 | 18              | 10  | -60                               | 8     | 15     | 2100                                   | E         | T4   |
| TWAD757*030□BEZ0^00                   | 750                          | 30                                 | 1                             | 3.6                 | 30              | 15  | -50                               | 8     | 15     | 2000                                   | D         | T3   |
| TWAE757*030□BEZ0^00                   | 750                          | 30                                 | 0.8                           | 5                   | 20              | 10  | -65                               | 10    | 18     | 2200                                   | E         | T4   |
| TWAD108*030□BSZ0^00                   | 1000                         | 30                                 | 0.7                           | 7                   | 25              | 7   | -70                               | 10    | 18     | 2500                                   | D         | T3   |
| TWAD108*030□BEZ0^00*                  | 1000                         | 30                                 | 0.7                           | 7                   | 25              | 7   | -70                               | 10    | 18     | 2500                                   | D         | T3   |
| TWAE108*030□BEZ0^00                   | 1000                         | 30                                 | 0.7                           | 5                   | 20              | 7   | -70                               | 10    | 18     | 2500                                   | E         | T4   |
| TWAE158*030□BSZ0^00                   | 1500                         | 30                                 | 0.6                           | 12                  | 35              | 6   | -72                               | 10    | 20     | 3000                                   | E         | T4   |
| <b>50 VDC at 85°C 30 VDC at 125°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAB476*050□BSZ0^00                   | 47                           | 50                                 | 3                             | 0.8                 | 8               | 70  | -28                               | 13    | 15     | 1155                                   | B         | T2   |
| TWAA686*050□BSZ0000                   | 68                           | 50                                 | 1.5                           | 1                   | 5               | 35  | -25                               | 8     | 15     | 1050                                   | A         | T1   |
| TWAA686*050□BEZ0^00*                  | 68                           | 50                                 | 2.5                           | 2                   | 10              | 45  | -25                               | 20    | 25     | 1050                                   | A         | T1   |
| TWAA107M050□BSZ0^00                   | 100                          | 50                                 | 5                             | 2                   | 15              | 70  | -45                               | 50    | 95     | 1500                                   | A         | T1   |
| TWAB127*050□BEZ0^00                   | 120                          | 50                                 | 2                             | 2                   | 10              | 40  | -45                               | 8     | 15     | 1200                                   | B         | T2   |
| TWAB157*050□BEZ0^00                   | 150                          | 50                                 | 2                             | 2                   | 10              | 25  | -50                               | 8     | 15     | 1400                                   | B         | T2   |
| TWAB227*050□BSZ0000                   | 220                          | 50                                 | 0.9                           | 2                   | 10              | 17.5                                      | -50                               | 8     | 15     | 1800                                   | B         | T2   |
| TWAB227*050□BEZ0^00*                  | 220                          | 50                                 | 0.9                           | 4                   | 20              | 17.5                                      | -50                               | 18    | 28     | 1800                                   | B         | T2   |
| TWAE337*050□BSZ0^00                   | 330                          | 50                                 | 0.8                           | 2.5                 | 25              | 15  | -50                               | 8     | 15     | 1900                                   | E         | T4   |
| TWAE337*050□BEZ0^00*                  | 330                          | 50                                 | 0.8                           | 2.5                 | 25              | 15  | -50                               | 8     | 15     | 1900                                   | E         | T4   |
| TWAD477*050□BSZ0^00                   | 470                          | 50                                 | 0.75                          | 3                   | 25              | 10  | -50                               | 8     | 15     | 2100                                   | D         | T3   |
| TWAD477*050□BEZ0^00*                  | 470                          | 50                                 | 1                             | 3                   | 25              | 11  | -50                               | 8     | 15     | 2100                                   | D         | T3   |
| TWAE477*050□BSZ0^00                   | 470                          | 50                                 | 0.75                          | 3                   | 30              | 10  | -50                               | 8     | 15     | 2200                                   | E         | T4   |
| TWAE477*050□BEZ0^00*                  | 470                          | 50                                 | 0.75                          | 3                   | 30              | 10  | -50                               | 8     | 15     | 2200                                   | E         | T4   |
| TWAE687*050□BSZ0^00                   | 680                          | 50                                 | 0.7                           | 5                   | 40              | 8   | -58                               | 10    | 20     | 2750                                   | E         | T4   |
| TWAE687*050□BEZ0^00*                  | 680                          | 50                                 | 0.7                           | 5                   | 40              | 8   | -58                               | 10    | 20     | 2750                                   | E         | T4   |
| TWAE757*050□BEZ0^00                   | 750                          | 50                                 | 0.6                           | 12                  | 60              | 8   | -50                               | 15    | 20     | 2800                                   | E         | T4   |
| TWAD108*050□BEZ0^00                   | 1000                         | 50                                 | 1.5                           | 20                  | 125             | 12  | -90                               | 100   | 140    | 2500                                   | D         | T3   |
| TWAE108*050□BSZ0^00                   | 1000                         | 50                                 | 1.0                           | 12                  | 90              | 20  | -90                               | 30    | 50     | 3200                                   | E         | T4   |
| TWAE108*050□BEZ0^00*                  | 1000                         | 50                                 | 0.7                           | 11                  | 110             | 20  | -70                               | 30    | 40     | 3200                                   | E         | T4   |
| TWAE128*050□BSZ0^00                   | 1200                         | 50                                 | 1.0                           | 12                  | 90              | 20  | -90                               | 30    | 50     | 3200                                   | E         | T4   |
| TWAE158*050□BSZ0^00                   | 1500                         | 50                                 | 1                             | 35                  | 130             | 6   | -75                               | 45    | 55     | 3500                                   | E         | T4   |
| TWAE308M050□BSZ0^00                   | 3000                         | 50                                 | 0.3                           | 30                  | 150             | 3.5                                       | -80                               | 60    | 85     | 3100                                   | E         | T4   |
| TWAE308M050□BEZ0^00*                  | 3000                         | 50                                 | 0.3                           | 30                  | 150             | 3.5                                       | -80                               | 60    | 85     | 3100                                   | E         | T4   |
| <b>60 VDC at 85°C 40 VDC at 125°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAA476*060□BSZ0000                   | 47                           | 60                                 | 2                             | 1                   | 5               | 44  | -25                               | 8     | 12     | 1050                                   | A         | T1   |
| TWAA476*060□BEZ0^00*                  | 47                           | 60                                 | 2                             | 2                   | 10              | 55  | -25                               | 15    | 25     | 1050                                   | A         | T1   |
| TWAB107*060□BEZ0^00                   | 100                          | 60                                 | 2.5                           | 1.7                 | 10              | 40  | -40                               | 8     | 15     | 1100                                   | B         | T2   |
| TWAB157*060□BSZ0000                   | 150                          | 60                                 | 1.1                           | 2                   | 10              | 20  | -40                               | 8     | 15     | 1650                                   | B         | T2   |
| TWAB157*060□BEZ0^00*                  | 150                          | 60                                 | 1.5                           | 2                   | 10              | 30  | -35                               | 12    | 20     | 1650                                   | B         | T2   |
| TWAD397*060□BSZ0^00                   | 390                          | 60                                 | 0.9                           | 3                   | 25              | 15  | -60                               | 8     | 15     | 2100                                   | D         | T3   |



# TWA Series



## COTS-Plus Wet Electrolytic Tantalum Capacitor

### RATINGS & PART NUMBER REFERENCE

| AVX Part Number                        | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | ESR Max<br>(Ohms)<br>at 120Hz | DC Leakage max (µA) |                 | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance Change<br>(%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |      |
|--|------------------------------|------------------------------------|-------------------------------|---------------------|-----------------|---|-----------------------------------|-------|--------|--|-----------|------|
|  |                              |                                    |                               | +25°C               | +85 &<br>+125°C |   | -55°C                             | +85°C | +125°C |  | AVX       | DSCC |
| TWAD397*060□BEZ0^00*                   | 390                          | 60                                 | 0.9                           | 3                   | 25              | 15  | -60                               | 8     | 15     | 2100                                   | D         | T3   |
| TWAE567*060□BSZ0^00                    | 560                          | 60                                 | 0.8                           | 5                   | 40              | 10  | -58                               | 8     | 15     | 2750                                   | E         | T4   |
| TWAE567*060□BEZ0^00*                   | 560                          | 60                                 | 0.8                           | 5                   | 40              | 10  | -58                               | 8     | 15     | 2750                                   | E         | T4   |
| TWAE687*060□BEZ0^00                    | 680                          | 60                                 | 0.6                           | 13                  | 65              | 8   | -50                               | 15    | 20     | 2800                                   | E         | T4   |
| TWAE757*060□BEZ0^00                    | 750                          | 60                                 | 0.6                           | 15                  | 75              | 8   | -50                               | 15    | 20     | 2800                                   | E         | T4   |
| TWAE108*060□BSZ0^00                    | 1000                         | 60                                 | 1                             | 12                  | 90              | 20  | -90                               | 30    | 50     | 3200                                   | E         | T4   |
| TWAE108*060□BEZ0^00*                   | 1000                         | 60                                 | 0.5                           | 20                  | 60              | 4.5                                       | -70                               | 30    | 60     | 3200                                   | E         | T4   |
| TWAE228M060□BEZ0^00                    | 2200                         | 60                                 | 0.5                           | 40                  | 120             | 3.0                                       | -80                               | 60    | 80     | 3000                                   | E         | T4   |
| <b>75 VDC at 85°C 50 VDC at 125°C</b>  |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAA336*075□BSZ0000                    | 33                           | 75                                 | 2.5                           | 1                   | 5               | 66  | -25                               | 5     | 9      | 1050                                   | A         | T1   |
| TWAA336*075□BEZ0^00*                   | 33                           | 75                                 | 2.5                           | 2                   | 10              | 70  | -25                               | 15    | 25     | 1050                                   | A         | T1   |
| TWAA686M075□BSZ0^00                    | 68                           | 75                                 | 5                             | 2                   | 15              | 70  | -45                               | 50    | 95     | 1500                                   | A         | T1   |
| TWAB107*075□BEZ0^00                    | 100                          | 75                                 | 2.5                           | 2                   | 10              | 40  | -35                               | 6     | 10     | 1400                                   | B         | T2   |
| TWAB117*075□BSZ0000                    | 110                          | 75                                 | 1.3                           | 2                   | 10              | 24  | -35                               | 6     | 10     | 1650                                   | B         | T2   |
| TWAB117*075□BEZ0^00*                   | 110                          | 75                                 | 1.5                           | 2                   | 10              | 30  | -35                               | 12    | 20     | 1650                                   | B         | T2   |
| TWAE227*075□BSZ0^00                    | 220                          | 75                                 | 1.1                           | 2.5                 | 30              | 20  | -50                               | 6     | 10     | 1800                                   | E         | T4   |
| TWAE227*075□BEZ0^00*                   | 220                          | 75                                 | 1.1                           | 2.5                 | 30              | 20  | -50                               | 6     | 10     | 1800                                   | E         | T4   |
| TWAD337*075□BSZ0^00                    | 330                          | 75                                 | 1                             | 3                   | 30              | 12  | -45                               | 6     | 10     | 2100                                   | D         | T3   |
| TWAD337*075□BEZ0^00*                   | 330                          | 75                                 | 1.2                           | 3                   | 30              | 15  | -60                               | 10    | 20     | 2100                                   | D         | T3   |
| TWAE337*075□BEZ0^00                    | 330                          | 75                                 | 1                             | 3                   | 40              | 12  | -50                               | 6     | 10     | 2200                                   | E         | T4   |
| TWAE477*075□BSZ0^00                    | 470                          | 75                                 | 0.9                           | 5                   | 50              | 12  | -55                               | 6     | 10     | 2750                                   | E         | T4   |
| TWAE477*075□BEZ0^00*                   | 470                          | 75                                 | 0.9                           | 5                   | 50              | 12  | -55                               | 6     | 10     | 2750                                   | E         | T4   |
| TWAE667*075□BSZ0^00                    | 660                          | 75                                 | 0.7                           | 12                  | 120             | 10  | -70                               | 30    | 40     | 2750                                   | E         | T4   |
| TWAE667*075□BEZ0^00                    | 680                          | 75                                 | 0.9                           | 11                  | 110             | 10  | -70                               | 30    | 40     | 2750                                   | E         | T4   |
| TWAE757*075□BSZ0^00                    | 750                          | 75                                 | 0.7                           | 12                  | 120             | 10  | -70                               | 30    | 40     | 3800                                   | E         | T4   |
| TWAE757*075□BEZ0^00*                   | 750                          | 75                                 | 0.7                           | 12                  | 120             | 10  | -70                               | 30    | 40     | 3800                                   | E         | T4   |
| TWAE108*075□BEZ0^00                    | 1000                         | 75                                 | 0.5                           | 30                  | 90              | 4.5                                       | -70                               | 30    | 60     | 3500                                   | E         | T4   |
| <b>100 VDC at 85°C 65 VDC at 125°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAA106M100□BSZ0^00                    | 10                           | 100                                | 3.5                           | 5                   | 25              | 190                                       | -18                               | 10    | 30     | 1050                                   | A         | T1   |
| TWAA156*100□BSZ0000                    | 15                           | 100                                | 3.5                           | 1                   | 5               | 125                                       | -18                               | 3     | 10     | 1050                                   | A         | T1   |
| TWAA156*100□BEZ0^00*                   | 15                           | 100                                | 5.5                           | 7                   | 35              | 140                                       | -18                               | 10    | 30     | 1050                                   | A         | T1   |
| TWAB226*100□BSZ0^00                    | 22                           | 100                                | 4                             | 1                   | 5               | 100                                       | -10                               | 8     | 15     | 1065                                   | B         | T2   |
| TWAB686*100□BSZ0000                    | 68                           | 100                                | 2.1                           | 2                   | 10              | 37  | -30                               | 4     | 12     | 1650                                   | B         | T2   |
| TWAB686*100□BEZ0^00*                   | 68                           | 100                                | 2.5                           | 2                   | 10              | 37  | -30                               | 4     | 12     | 1650                                   | B         | T2   |
| TWAD157*100□BSZ0^00                    | 150                          | 100                                | 1.6                           | 3                   | 25              | 22  | -35                               | 6     | 12     | 2100                                   | D         | T3   |
| TWAD157*100□BEZ0^00*                   | 150                          | 100                                | 1.6                           | 3                   | 25              | 22  | -35                               | 6     | 12     | 2100                                   | D         | T3   |
| TWAD227*100□BEZ0^00                    | 220                          | 100                                | 1.4                           | 5                   | 25              | 18  | -50                               | 10    | 15     | 2500                                   | D         | T3   |
| TWAE227*100□BSZ0^00                    | 220                          | 100                                | 1.2                           | 5                   | 50              | 15  | -40                               | 6     | 12     | 2750                                   | E         | T4   |
| TWAE227*100□BEZ0^00*                   | 220                          | 100                                | 1.2                           | 5                   | 50              | 15  | -40                               | 6     | 12     | 2750                                   | E         | T4   |
| TWAE337*100□BSZ0^00                    | 330                          | 100                                | 0.8                           | 6                   | 60              | 10  | -45                               | 7     | 20     | 3600                                   | E         | T4   |
| TWAE337*100□BEZ0^00*                   | 330                          | 100                                | 0.8                           | 6                   | 60              | 10  | -45                               | 7     | 20     | 3600                                   | E         | T4   |
| TWAE407*100□BSZ0^00                    | 400                          | 100                                | 0.8                           | 10                  | 150             | 10  | -50                               | 10    | 35     | 4100                                   | E         | T4   |
| TWAE407*100□BEZ0^00*                   | 400                          | 100                                | 0.8                           | 10                  | 150             | 10  | -50                               | 10    | 35     | 4100                                   | E         | T4   |
| TWAE477*100□BSZ0^00                    | 470                          | 100                                | 0.7                           | 15                  | 150             | 10  | -50                               | 10    | 35     | 4100                                   | E         | T4   |
| TWAE477*100□BEZ0^00*                   | 470                          | 100                                | 0.7                           | 15                  | 150             | 10  | -50                               | 10    | 35     | 4100                                   | E         | T4   |
| TWAE567*100□BSZ0^00                    | 560                          | 100                                | 1.0                           | 25                  | 200             | 10  | -60                               | 45    | 110    | 4100                                   | E         | T4   |
| TWAE757*100□BEZ0^00                    | 750                          | 100                                | 0.6                           | 30                  | 150             | 5   | -60                               | 50    | 120    | 4200                                   | E         | T4   |
| <b>125 VDC at 85°C 85 VDC at 125°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |
| TWAA106*125□BSZ0000                    | 10                           | 125                                | 5.5                           | 1                   | 5               | 175                                       | -15                               | 3     | 10     | 1050                                   | A         | T1   |
| TWAA106M125□BEZ0^00*                   | 10                           | 125                                | 5.5                           | 1                   | 5               | 190                                       | -15                               | 10    | 30     | 1050                                   | A         | T1   |
| TWAB276*125□BSZ0^00                    | 27                           | 125                                | 4                             | 2                   | 10              | 100                                       | -10                               | 8     | 15     | 1200                                   | B         | T2   |
| TWAB476*125□BSZ0000                    | 47                           | 125                                | 2.3                           | 2                   | 10              | 47  | -25                               | 5     | 12     | 1650                                   | B         | T2   |
| TWAB476*125□BEZ0^00*                   | 47                           | 125                                | 2.3                           | 2                   | 10              | 47  | -25                               | 5     | 12     | 1650                                   | B         | T2   |
| TWAE826*125□BSZ0^00                    | 82                           | 125                                | 1.6                           | 2                   | 10              | 39  | -24                               | 10    | 20     | 1900                                   | E         | T4   |
| TWAD107*125□BSZ0^00                    | 100                          | 125                                | 1.8                           | 3                   | 25              | 35  | -35                               | 5     | 12     | 2100                                   | D         | T3   |
| TWAD107*125□BEZ0^00*                   | 100                          | 125                                | 1.8                           | 3                   | 25              | 35  | -35                               | 5     | 12     | 2100                                   | D         | T3   |
| TWAD127*125□BEZ0^00                    | 120                          | 125                                | 1.8                           | 3                   | 25              | 35  | -35                               | 5     | 12     | 2100                                   | D         | T3   |
| TWAE157*125□BSZ0^00                    | 150                          | 125                                | 1.6                           | 5                   | 50              | 20  | -35                               | 6     | 12     | 2750                                   | E         | T4   |
| TWAE157*125□BEZ0^00*                   | 150                          | 125                                | 1.6                           | 5                   | 50              | 20  | -35                               | 6     | 16     | 2750                                   | E         | T4   |
| TWAE227*125□BEZ0^00                    | 220                          | 125                                | 1.4                           | 10                  | 50              | 12  | -40                               | 8     | 15     | 3600                                   | E         | T4   |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.

DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

\*Not recommended for new designs, for new design use part number with Inspection level "S" – COTS-Plus

$$DF = 2\pi f \times (ESR)$$

$$2\pi = 6.28$$

$$f = 120\text{Hz}$$

C = Actual measured capacitance

ESR = Actual measured ESR

# TWA-Y 200°C Series



## Wet Electrolytic Tantalum Capacitor



The TWA-Y series represents a high temperature version of conventional wet electrolytic tantalum capacitors that are designed for use at 200°C. High capacitance cathode system allows high level of CV (Capacitance/Voltage) in standard case sizes.


Selected values of the TWA-Y are capable of up to 2000 hours of operation at extreme temperatures with the applicable derated voltage.

Mechanical testing being conducted in accordance to MIL-STD- 202, High Frequency vibration - method 204, test condition "D" Mechanical Shock Test - method 213, test condition "I".

This design includes a welded tantalum can and header assembly that provides a hermetic seal to withstand also harsh shock and vibration requirements.

Contact the factory for additional options for customized component design.

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)

| DSCC Case Size | AVX Case Size | L<br>+0.79 (0.031)<br>-0.41 (0.016) | D  |                               | E<br>±6.35 (0.250) |
|----------------|---------------|-------------------------------------|--|-------------------------------|--------------------|
|                |               |                                     | Without Insulating Sleeve<br>±0.41 (0.016) | With Insulating Sleeve<br>Max |                    |
| T1             | A             | 11.51 (0.453)                       | 4.78 (0.188)                               | 5.56 (0.219)                  | 38.10 (1.500)      |
| T2             | B             | 16.28 (0.641)                       | 7.14 (0.281)                               | 7.92 (0.312)                  | 57.15 (2.250)      |
| T3             | D             | 19.46 (0.766)                       | 9.52 (0.375)                               | 10.31 (0.406)                 | 57.15 (2.250)      |
| T4             | E             | 26.97 (1.062)                       | 9.52 (0.375)                               | 10.31 (0.406)                 | 57.15 (2.250)      |

### VOLTAGE RATINGS (Operating Temperature -55°C to 200°C)

| Voltage (DC)                                |       |    |    |    |    |    |    |     |     |
|---|-------|----|----|----|----|----|----|-----|-----|
| Rated Voltage: (V <sub>R</sub> )            | 85°C  | 15 | 25 | 30 | 50 | 60 | 75 | 100 | 125 |
| Derated Voltage: (V <sub>C</sub> )          | 125°C | 10 | 15 | 20 | 30 | 40 | 50 | 65  | 85  |
| High Temperature Voltage: (V <sub>T</sub> ) | 200°C | 9  | 12 | 18 | 30 | 36 | 45 | 60  | 75  |



# TWA-Y 200°C Series





## Wet Electrolytic Tantalum Capacitor

### HOW TO ORDER

#### AVX PART NUMBER:

|            |           |  |   |              |  |                            |                                |                           |                                |  |                                      |
|------------|-----------|--|---|--------------|--|----------------------------|--------------------------------|---------------------------|--------------------------------|--|--------------------------------------|
| <b>TWA</b> | <b>E</b>  | <b>757</b>   | <b>*</b>                                      | <b>075</b>   | <b>□</b>   | <b>B</b>                   | <b>Y</b>                       | <b>Z</b>                  | <b>0</b>                       | <b>^</b>   | <b>00</b>                            |
| Type       | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>K = ±10%<br>M = ±20% | Voltage Code | Insulation Sleeve<br>C = Without Sleeve<br>S = With Sleeve | Packaging<br>B = Tray Pack | Qualification<br>Y = High Temp | Reliability<br>Z = Non-ER | Qualification Level<br>0 = N/A | Termination Finish<br>0 = Sn/Pb 60/40<br>7 = Matte tin | Custom Test Options<br>00 = Standard |

LEAD-FREE  
LEAD-FREE COMPATIBLE COMPONENT

RoHS  
COMPLIANT

For RoHS compliant products, please select correct termination style.

### RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/</sup>

| Frequency of Applied Ripple Current |         | 120Hz |      |      |      | 800Hz |      |      |      | 1kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |
| % of                                | 100%    | 0.60  | 0.39 | –    | –    | 0.71  | 0.43 | –    | –    | 0.72 | 0.45 | –    | –    |
|                                     | 85°C    | 0.60  | 0.46 | –    | –    | 0.71  | 0.55 | –    | –    | 0.72 | 0.55 | –    | –    |
| Rated                               | 80%     | 0.60  | 0.52 | 0.35 | –    | 0.71  | 0.62 | 0.42 | –    | 0.72 | 0.62 | 0.42 | –    |
|                                     | 70%     | 0.60  | 0.58 | 0.44 | –    | 0.71  | 0.69 | 0.52 | –    | 0.72 | 0.70 | 0.52 | –    |
| Peak                                | 66-2/3% | 0.60  | 0.60 | 0.46 | 0.27 | 0.71  | 0.71 | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |

| Frequency of Applied Ripple Current |         | 10kHz |      |      |      | 40kHz |      |      |      | 100kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|--------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |
| % of                                | 100%    | 0.88  | 0.55 | –    | –    | 1.00  | 0.63 | –    | –    | 1.10   | 0.69 | –    | –    |
|                                     | 85°C    | 0.88  | 0.67 | –    | –    | 1.00  | 0.77 | –    | –    | 1.10   | 0.85 | –    | –    |
| Rated                               | 80%     | 0.88  | 0.76 | 0.52 | –    | 1.00  | 0.87 | 0.59 | –    | 1.10   | 0.96 | 0.65 | –    |
|                                     | 70%     | 0.88  | 0.85 | 0.64 | –    | 1.00  | 0.97 | 0.73 | –    | 1.10   | 1.07 | 0.80 | –    |
| Peak                                | 66-2/3% | 0.88  | 0.88 | 0.68 | 0.40 | 1.00  | 1.00 | 0.77 | 0.45 | 1.10   | 1.10 | 0.85 | 0.50 |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.



# TWA-Y 200°C Series



## Wet Electrolytic Tantalum Capacitor

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) to 85°C |                  |     |                  |     |                  |                  |                  |
|-------------|------|--|------------------|-----|------------------|-----|------------------|------------------|------------------|
| µF          | Code | 15V  | 25V              | 30V | 50V              | 60V | 75V              | 100V             | 125V             |
| 10          | 106  |  |                  |     | A                |     |                  | A <sup>(M)</sup> | A <sup>(M)</sup> |
| 15          | 156  |  |                  | A   |                  |     |                  | A                |                  |
| 22          | 226  |  | A                |     |                  | A   | A                | B                |                  |
| 27          | 276  |  |                  |     |                  | A   |                  |                  | B                |
| 33          | 336  | A  |                  |     | A                |     | A                |                  |                  |
| 47          | 476  |  |                  |     | B                | A   |                  |                  | B                |
| 50          | 506  |  |                  |     |                  | B   |                  |                  |                  |
| 56          | 566  |  | A                | A   |                  |     | B                |                  |                  |
| 60          | 606  |  |                  |     | B                |     |                  |                  |                  |
| 68          | 686  |  | A                |     | A                | B   | A <sup>(M)</sup> | B                |                  |
| 82          | 826  |  |                  |     | B                |     | B                |                  | D,E              |
| 100         | 107  |  | B                | A,B | A <sup>(M)</sup> |     |                  |                  | D                |
| 110         | 117  |  |                  |     |                  | B   | B                |                  |                  |
| 120         | 127  |  | A,B              |     | B                |     |                  |                  |                  |
| 150         | 157  |  |                  | B   |                  | B   |                  | D                | E                |
| 180         | 187  |  |                  |     |                  |     | D                |                  |                  |
| 220         | 227  |  |                  | B   | B                | D   | E                | E                | E                |
| 270         | 277  |  | B                |     | D                | E   |                  |                  |                  |
| 300         | 307  |  |                  | D   |                  |     |                  |                  |                  |
| 330         | 337  |  |                  |     | E                |     |                  | E                |                  |
| 390         | 397  | D  |                  | D   |                  |     |                  |                  |                  |
| 400         | 407  |  |                  |     |                  |     |                  | E                |                  |
| 470         | 477  |  |                  | B,D |                  |     | E                | E                |                  |
| 560         | 567  |  | B,E              | E   |                  |     |                  | E                |                  |
| 680         | 687  |  |                  |     |                  |     | E                |                  |                  |
| 750         | 757  |  |                  |     |                  |     | E                | E                |                  |
| 1000        | 108  |  |                  | D   | E                | E   | E                |                  |                  |
| 1200        | 128  |  | D                |     |                  |     |                  |                  |                  |
| 1500        | 158  |  |                  |     | E                |     |                  |                  |                  |
| 3000        | 308  |  | E <sup>(M)</sup> |     |                  |     |                  |                  |                  |

Available Ratings (M tolerance only)

Engineering samples - please contact manufacturer

### RATINGS & PART NUMBER REFERENCE

| AVX Part Number                                | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | ESR Max<br>(Ohms)<br>at 120Hz | DC Leakage max (µA) |                 | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance Change<br>(%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |      | Lifetime at<br>200°C (hrs.) |
|--|------------------------------|------------------------------------|-------------------------------|---------------------|-----------------|---|-----------------------------------|-------|--------|--|-----------|------|-----------------------------|
|  |                              |                                    |                               | +25°C               | +85 &<br>+125°C |   | -55°C                             | +85°C | +125°C |  | AVX       | DSCC |                             |
| 15 VDC at 85°C 10 VDC at 125°C 9 VDC at 200°C  |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA336*015□BYZ0^00                            | 33                           | 15                                 | 4                             | 1                   | 2               | 90  | -28                               | 14    | 16     | 820                                    | A         | T1   | 2000                        |
| TWAD397*015□BYZ0^00                            | 390                          | 15                                 | 1.7                           | 7                   | 28              | 48  | -70                               | 25    | 25     | 1396                                   | D         | T3   | 1000                        |
| 25 VDC at 85°C 15 VDC at 125°C 12 VDC at 200°C |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA226*025□BYZ0^00                            | 22                           | 25                                 | 4                             | 1                   | 2               | 140                                       | -20                               | 10.5  | 12     | 825                                    | A         | T1   | 2000                        |
| TWAA566*025□BYZ0^00                            | 56                           | 25                                 | 4                             | 1                   | 2               | 140                                       | -20                               | 10.5  | 12     | 825                                    | A         | T1   | 500                         |
| TWAA686*025□BYZ0^00                            | 68                           | 25                                 | 4                             | 1                   | 2               | 140                                       | -20                               | 10.5  | 12     | 825                                    | A         | T1   | 500                         |
| TWAB107*025□BYZ0^00                            | 100                          | 25                                 | 2.5                           | 1                   | 10              | 60  | -35                               | 13    | 15     | -                                      | B         | T2   | 2000                        |
| TWAA127*025□BYZ0^00                            | 120                          | 25                                 | 2.3                           | 2                   | 10              | 35  | -42                               | 20    | 25     | 1250                                   | A         | T1   | 500                         |
| TWAB127*025□BYZ0^00                            | 120                          | 25                                 | 2.3                           | 2                   | 10              | 60  | -32                               | 13    | 15     | -                                      | B         | T2   | 500                         |
| TWAB277*025□BYZ0^00                            | 270                          | 25                                 | 0.9                           | 4                   | 20              | 17.5                                      | -50                               | 18    | 28     | 1800                                   | B         | T2   | 1000                        |
| TWAB567*025□BYZ0^00                            | 560                          | 25                                 | 1.0                           | 2                   | 10              | 12  | -65                               | 10    | 15     | 2100                                   | B         | T2   | 1000                        |
| TWAE567*025□BYZ0^00                            | 560                          | 25                                 | 1.3                           | 9                   | 36              | 25  | -65                               | 25    | 30     | -                                      | E         | T4   | 2000                        |
| TWAD128*025□BYZ0^00                            | 1200                         | 25                                 | 0.65                          | 5                   | 20              | 7   | -70                               | 12    | 18     | 2600                                   | D         | T3   | 1000                        |
| TWAE308M025□BYZ0^00                            | 3000                         | 25                                 | 0.5                           | 15                  | 30              | 3.5                                       | -80                               | 60    | 85     | 3100                                   | E         | T4   | 500                         |
| 30 VDC at 85°C 20 VDC at 125°C 18 VDC at 200°C |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA156*030□BYZ0^00                            | 15                           | 30                                 | 4.4                           | 1                   | 2               | 200                                       | -20                               | 10.5  | 16     | -                                      | A         | T1   | 2000                        |
| TWAA566*030□BYZ0^00                            | 56                           | 30                                 | 5.2                           | 2                   | 9               | 200                                       | -48                               | 12    | 15     | -                                      | A         | T1   | 2000                        |
| TWAA107*030□BYZ0^00                            | 100                          | 30                                 | 2.3                           | 2                   | 10              | 35  | -38                               | 20    | 25     | 1200                                   | A         | T1   | 500                         |
| TWAB107*030□BYZ0^00                            | 100                          | 30                                 | 2.3                           | 2                   | 12              | 60  | -30                               | 10.5  | 12     | -                                      | B         | T2   | 500                         |



# TWA-Y 200°C Series



## Wet Electrolytic Tantalum Capacitor

### RATINGS & PART NUMBER REFERENCE

| AVX Part Number  | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | ESR Max<br>(Ohms)<br>at 120Hz | DC Leakage max (µA) |                 | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance Change<br>(%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |      | Lifetime at<br>200°C (hrs.) |
|--|------------------------------|------------------------------------|-------------------------------|---------------------|-----------------|---|-----------------------------------|-------|--------|--|-----------|------|-----------------------------|
|  |                              |                                    |                               | +25°C               | +85 &<br>+125°C |   | -55°C                             | +85°C | +125°C |  | AVX       | DSCC |                             |
| TWAB157*030□BYZ0^00                                    | 150                          | 30                                 | 2.5                           | 2                   | 18              | 40  | -48                               | 13    | 15     | 1100                                   | B         | T2   | 2000                        |
| TWAB227*030□BYZ0^00                                    | 220                          | 30                                 | 0.9                           | 4                   | 20              | 17.5                                      | -50                               | 18    | 28     | 1800                                   | B         | T2   | 1000                        |
| TWAD307*030□BYZ0^00                                    | 300                          | 30                                 | 1.8                           | 8                   | 32              | 25  | -51                               | 20    | 25     | -                                      | D         | T3   | 2000                        |
| TWAD397*030□BYZ0^00                                    | 390                          | 30                                 | 1.8                           | 6                   | 18              | 25  | -65                               | 18    | 25     | -                                      | D         | T3   | 2000                        |
| TWAB477*030□BYZ0^00                                    | 470                          | 30                                 | 1.0                           | 2                   | 10              | 15  | -65                               | 10    | 18     | 1800                                   | B         | T2   | 1000                        |
| TWAD477*030□BYZ0^00                                    | 470                          | 30                                 | 1.0                           | 3                   | 25              | 15  | -65                               | 15    | 25     | 1600                                   | D         | T3   | 2000                        |
| TWAE567*030□BYZ0^00                                    | 560                          | 30                                 | 1.3                           | 9                   | 36              | 25  | -65                               | 25    | 30     | -                                      | E         | T4   | 2000                        |
| TWAD108*030□BYZ0^00                                    | 1000                         | 30                                 | 0.7                           | 7                   | 25              | 7   | -70                               | 10    | 18     | 2500                                   | D         | T3   | 1000                        |
| <b>50 VDC at 85°C 30 VDC at 125°C 30 VDC at 200°C</b>  |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA106*050□BYZ0^00                                    | 10                           | 50                                 | 5.3                           | 1                   | 2               | 250                                       | -24                               | 8     | 9      | 715                                    | A         | T1   | 2000                        |
| TWAA336*050□BYZ0^00                                    | 33                           | 50                                 | 5                             | 2                   | 9               | 200                                       | -39                               | 10    | 12     | -                                      | A         | T1   | 2000                        |
| TWAB476*050□BYZ0^00                                    | 47                           | 50                                 | 3                             | 0.8                 | 8               | 70  | -28                               | 13    | 15     | 1155                                   | B         | T2   | 500                         |
| TWAB606*050□BYZ0^00                                    | 60                           | 50                                 | 2.6                           | 2                   | 12              | 60  | -30                               | 10.5  | 12     | -                                      | B         | T2   | 500                         |
| TWAA686*050□BYZ0^00                                    | 68                           | 50                                 | 2.5                           | 2                   | 10              | 45  | -25                               | 20    | 25     | 1050                                   | A         | T1   | 1000                        |
| TWAB826*050□BYZ0^00                                    | 82                           | 50                                 | 2.4                           | 2                   | 16              | 60  | -32                               | 13    | 15     | -                                      | B         | T2   | 500                         |
| TWAA107M050□BYZ0^00                                    | 100                          | 50                                 | 5                             | 2                   | 15              | 70  | -45                               | 50    | 95     | 1500                                   | A         | T1   | 500                         |
| TWAB127*050□BYZ0^00                                    | 120                          | 50                                 | 2.5                           | 4                   | 24              | 40  | -42                               | 12    | 15     | -                                      | B         | T2   | 2000                        |
| TWAB227*050□BYZ0^00                                    | 220                          | 50                                 | 0.9                           | 4                   | 20              | 17.5                                      | -50                               | 18    | 28     | 1800                                   | B         | T2   | 1000                        |
| TWAD277*050□BYZ0^00                                    | 270                          | 50                                 | 1.8                           | 8                   | 32              | 25  | -51                               | 20    | 25     | -                                      | D         | T3   | 2000                        |
| TWAE377*050□BYZ0^00                                    | 330                          | 50                                 | 1.5                           | 9                   | 36              | 25  | -46                               | 25    | 30     | 1900                                   | E         | T4   | 2000                        |
| TWAE108*050□BYZ0^00                                    | 1000                         | 50                                 | 0.7                           | 11                  | 110             | 20  | -70                               | 30    | 40     | 3200                                   | E         | T4   | 500                         |
| TWAE158*050□BYZ0^00                                    | 1500                         | 50                                 | 1                             | 35                  | 130             | 6   | -75                               | 45    | 55     | 3500                                   | E         | T4   | 1000                        |
| <b>60 VDC at 85°C 40 VDC at 125°C 36 VDC at 200°C</b>  |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA226*060□BYZ0^00                                    | 22                           | 60                                 | 5                             | 3                   | 12              | 200                                       | -34                               | 10    | 12     | 500                                    | A         | T1   | 2000                        |
| TWAA276*060□BYZ0^00                                    | 27                           | 60                                 | 5                             | 3                   | 12              | 200                                       | -34                               | 10    | 12     | -                                      | A         | T1   | 2000                        |
| TWAA476*060□BYZ0^00                                    | 47                           | 60                                 | 2                             | 2                   | 10              | 55  | -25                               | 15    | 25     | 1050                                   | A         | T1   | 500                         |
| TWAB506*060□BYZ0^00                                    | 50                           | 60                                 | 2.6                           | 2                   | 12              | 60  | -30                               | 10.5  | 12     | -                                      | B         | T2   | 500                         |
| TWAB686*060□BYZ0^00                                    | 68                           | 60                                 | 2.5                           | 2                   | 16              | 60  | -32                               | 10.5  | 12     | -                                      | B         | T2   | 500                         |
| TWAB107*060□BYZ0^00                                    | 100                          | 60                                 | 2.5                           | 1.7                 | 10              | 40  | -40                               | 8     | 15     | 1100                                   | B         | T2   | 2000                        |
| TWAB157*060□BYZ0^00                                    | 150                          | 60                                 | 1.5                           | 2                   | 10              | 30  | -35                               | 12    | 20     | 1650                                   | B         | T2   | 500                         |
| TWAD227*060□BYZ0^00                                    | 220                          | 60                                 | 1.8                           | 8                   | 32              | 25  | -45                               | 16    | 20     | -                                      | D         | T3   | 2000                        |
| TWAE277*060□BYZ0^00                                    | 270                          | 60                                 | 1.3                           | 9                   | 36              | 25  | -45                               | 20    | 25     | -                                      | E         | T4   | 2000                        |
| TWAE108*060□BYZ0^00                                    | 1000                         | 60                                 | 0.5                           | 20                  | 60              | 4.5                                       | -70                               | 30    | 60     | 3200                                   | E         | T4   | 1000                        |
| <b>75 VDC at 85°C 50 VDC at 125°C 45 VDC at 200°C</b>  |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA226*075□BYZ0^00                                    | 22                           | 75                                 | 5.1                           | 3                   | 12              | 157                                       | -19                               | 10    | 12     | 600                                    | A         | T1   | 2000                        |
| TWAA336*075□BYZ0^00                                    | 33                           | 75                                 | 2.5                           | 2                   | 10              | 70  | -25                               | 15    | 25     | 1050                                   | A         | T1   | 1000                        |
| TWAB566*075□BYZ0^00                                    | 56                           | 75                                 | 2.6                           | 2                   | 17              | 60  | -30                               | 10.5  | 15     | -                                      | B         | T2   | 500                         |
| TWAA686M075□BYZ0^00                                    | 68                           | 75                                 | 5                             | 2                   | 15              | 70  | -45                               | 50    | 95     | 1500                                   | A         | T1   | 500                         |
| TWAB826*075□BYZ0^00                                    | 82                           | 75                                 | 2.5                           | 4                   | 24              | 37  | -30                               | 12    | 15     | -                                      | B         | T2   | 500                         |
| TWAB117*075□BYZ0^00                                    | 110                          | 75                                 | 1.5                           | 2                   | 10              | 30  | -35                               | 12    | 20     | 1650                                   | B         | T2   | 500                         |
| TWAD187*075□BYZ0^00                                    | 180                          | 75                                 | 2.2                           | 9                   | 36              | 25  | -40                               | 16    | 20     | -                                      | D         | T3   | 2000                        |
| TWAE227*075□BYZ0^00                                    | 220                          | 75                                 | 1.2                           | 5                   | 50              | 20  | -40                               | 8     | 15     | 1800                                   | E         | T4   | 2000                        |
| TWAE477*075□BYZ0^00                                    | 470                          | 75                                 | 0.9                           | 10                  | 125             | 10  | -50                               | 10    | 35     | 2750                                   | E         | T4   | 1000                        |
| TWAE687*075□BYZ0^00                                    | 680                          | 75                                 | 0.9                           | 11                  | 110             | 10  | -70                               | 30    | 40     | 2750                                   | E         | T4   | 500                         |
| TWAE757*075□BYZ0^00                                    | 750                          | 75                                 | 0.7                           | 12                  | 120             | 10  | -70                               | 30    | 40     | 3800                                   | E         | T4   | 500                         |
| TWAE108*075□BYZ0^00                                    | 1000                         | 75                                 | 0.5                           | 30                  | 90              | 4.5                                       | -70                               | 30    | 60     | 3500                                   | E         | T4   | 1000                        |
| <b>100 VDC at 85°C 65 VDC at 125°C 60 VDC at 200°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA106M100□BYZ0^00                                    | 10                           | 100                                | 3.5                           | 5                   | 25              | 190                                       | -18                               | 10    | 30     | 1050                                   | A         | T1   | 2000                        |
| TWAA156*100□BYZ0^00                                    | 15                           | 100                                | 5.5                           | 7                   | 35              | 140                                       | -18                               | 10    | 30     | 1050                                   | A         | T1   | 500                         |
| TWAB226*100□BYZ0^00                                    | 22                           | 100                                | 4                             | 1                   | 5               | 100                                       | -10                               | 8     | 15     | 1065                                   | B         | T2   | 500                         |
| TWAB686*100□BYZ0^00                                    | 68                           | 100                                | 2.5                           | 2                   | 10              | 37  | -30                               | 4     | 12     | 1650                                   | B         | T2   | 500                         |
| TWAD157*100□BYZ0^00                                    | 150                          | 100                                | 1.6                           | 3                   | 25              | 22  | -35                               | 6     | 12     | 2100                                   | D         | T3   | 2000                        |
| TWAE227*100□BYZ0^00                                    | 220                          | 100                                | 1.2                           | 5                   | 50              | 15  | -40                               | 6     | 12     | 2750                                   | E         | T4   | 2000                        |
| TWAE337*100□BYZ0^00                                    | 330                          | 100                                | 0.8                           | 6                   | 60              | 10  | -45                               | 7     | 20     | 3600                                   | E         | T4   | 2000                        |
| TWAE407*100□BYZ0^00                                    | 400                          | 100                                | 0.8                           | 10                  | 150             | 10  | -50                               | 10    | 35     | 4100                                   | E         | T4   | 2000                        |
| TWAE477*100□BYZ0^00                                    | 470                          | 100                                | 0.7                           | 15                  | 150             | 10  | -50                               | 10    | 35     | 4100                                   | E         | T4   | 2000                        |
| TWAE567*100□BYZ0^00                                    | 560                          | 100                                | 1.0                           | 25                  | 200             | 10  | -60                               | 45    | 110    | 4100                                   | E         | T4   | 1500                        |
| TWAE757*100□BYZ0^00                                    | 750                          | 100                                | 0.6                           | 30                  | 150             | 5   | -60                               | 50    | 120    | 4200                                   | E         | T4   | 500                         |
| <b>125 VDC at 85°C 85 VDC at 125°C 75 VDC at 200°C</b> |                              |                                    |                               |                     |                 |   |                                   |       |        |  |           |      |                             |
| TWAA106M125□BYZ0^00                                    | 10                           | 125                                | 5.5                           | 1                   | 5               | 190                                       | -15                               | 10    | 30     | 1050                                   | A         | T1   | 2000                        |
| TWAB276*125□BYZ0^00                                    | 27                           | 125                                | 4                             | 2                   | 10              | 100                                       | -10                               | 8     | 15     | 1200                                   | B         | T2   | 500                         |
| TWAB476*125□BYZ0^00                                    | 47                           | 125                                | 2.3                           | 2                   | 10              | 47  | -25                               | 5     | 12     | 1650                                   | B         | T2   | 1000                        |
| TWAD826*125□BYZ0^00                                    | 82                           | 125                                | 2.8                           | 12                  | 48              | 50  | -30                               | 15    | 17     | -                                      | D         | T3   | 2000                        |
| TWAE826*125□BYZ0^00                                    | 82                           | 125                                | 1.6                           | 2                   | 10              | 39  | -24                               | 10    | 20     | 1900                                   | E         | T4   | 2000                        |
| TWAD107*125□BYZ0^00                                    | 100                          | 125                                | 1.8                           | 3                   | 25              | 35  | -35                               | 5     | 12     | 2100                                   | D         | T3   | 2000                        |
| TWAE157*125□BYZ0^00                                    | 150                          | 125                                | 1.6                           | 5                   | 50              | 20  | -35                               | 6     | 16     | 2750                                   | E         | T4   | 2000                        |
| TWAE227*125□BYZ0^00                                    | 220                          | 125                                | 1.4                           | 10                  | 50              | 12  | -40                               | 8     | 15     | 3600                                   | E         | T4   | 2000                        |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.

DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

\*Not recommended for new designs, for new design use part number with Inspection level "S" – COTS-Plus

$$DF = 2\pi f \times (ESR)$$

$$2\pi = 6.28$$

$$f = 120\text{Hz}$$

C = Actual measured capacitance

ESR = Actual measured ESR

# TWA-X Series with Extension to 230°C

## Wet Electrolytic Tantalum Capacitor



The TWA-X series represents a high temperature version of conventional wet electrolytic tantalum capacitors that are designed for use at 230°C. High capacitance cathode system allows high level of CV (Capacitance/Voltage) in standard case sizes.


Selected values of the TWA-X are capable of up to 500 hours of operation at extreme temperatures with the applicable derated voltage.

Mechanical testing being conducted in accordance to MIL-STD- 202, High Frequency vibration - method 204, test condition "D" Mechanical Shock Test - method 213, test condition "I".

This design includes a welded tantalum can and header assembly that provides a hermetic seal to withstand also harsh shock and vibration requirements.

Contact the factory for additional options for customized component design.

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)

| DSCC Case Size | AVX Case Size | L                              | D  |                            | E             |
|----------------|---------------|--------------------------------|--|----------------------------|---------------|
|                |               |                                | Without Insulating Sleeve                  | With Insulating Sleeve Max |               |
| T4             | E             | +0.79 (0.031)<br>-0.41 (0.016) | Without Insulating Sleeve<br>±0.41 (0.016) | With Insulating Sleeve Max | ±6.35 (0.250) |
|                |               | 26.97 (1.062)                  | 9.52 (0.375)                               | 10.31 (0.406)              | 57.15 (2.250) |



# TWA-X Series with Extension to 230°C

## Wet Electrolytic Tantalum Capacitor

### HOW TO ORDER

#### AVX PART NUMBER:

|            |           |  |   |              |  |                            |  |                           |                                |  |                                      |
|------------|-----------|--|---|--------------|--|----------------------------|--|---------------------------|--------------------------------|--|--------------------------------------|
| <b>TWA</b> | <b>E</b>  | <b>407</b>   | <b>*</b>                                      | <b>100</b>   | <b>□</b>   | <b>B</b>                   | <b>X</b>                                   | <b>Z</b>                  | <b>0</b>                       | <b>^</b>   | <b>00</b>                            |
| Type       | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>K = ±10%<br>M = ±20% | Voltage Code | Insulation Sleeve<br>C = Without Sleeve<br>S = With Sleeve | Packaging<br>B = Tray Pack | Qualification<br>X = High-Temp up to 230°C | Reliability<br>Z = Non-ER | Qualification Level<br>0 = N/A | Termination Finish<br>0 = Sn/Pb 60/40<br>7 = Matte tin | Custom Test Options<br>00 = Standard |

For RoHS compliant products, please select correct termination style.

### RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/</sup>

| Frequency of Applied Ripple Current |         | 120Hz |      |      |      | 800Hz |      |      |      | 1kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |
| % of                                | 100%    | 0.60  | 0.39 | –    | –    | 0.71  | 0.43 | –    | –    | 0.72 | 0.45 | –    | –    |
|                                     | 85°C    | 0.60  | 0.46 | –    | –    | 0.71  | 0.55 | –    | –    | 0.72 | 0.55 | –    | –    |
| Rated                               | 80%     | 0.60  | 0.52 | 0.35 | –    | 0.71  | 0.62 | 0.42 | –    | 0.72 | 0.62 | 0.42 | –    |
|                                     | 70%     | 0.60  | 0.58 | 0.44 | –    | 0.71  | 0.69 | 0.52 | –    | 0.72 | 0.70 | 0.52 | –    |
| Peak                                | 66-2/3% | 0.60  | 0.60 | 0.46 | 0.27 | 0.71  | 0.71 | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |

| Frequency of Applied Ripple Current |         | 10kHz |      |      |      | 40kHz |      |      |      | 100kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|--------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |
| % of                                | 100%    | 0.88  | 0.55 | –    | –    | 1.00  | 0.63 | –    | –    | 1.10   | 0.69 | –    | –    |
|                                     | 85°C    | 0.88  | 0.67 | –    | –    | 1.00  | 0.77 | –    | –    | 1.10   | 0.85 | –    | –    |
| Rated                               | 80%     | 0.88  | 0.76 | 0.52 | –    | 1.00  | 0.87 | 0.59 | –    | 1.10   | 0.96 | 0.65 | –    |
|                                     | 70%     | 0.88  | 0.85 | 0.64 | –    | 1.00  | 0.97 | 0.73 | –    | 1.10   | 1.07 | 0.80 | –    |
| Peak                                | 66-2/3% | 0.88  | 0.88 | 0.68 | 0.40 | 1.00  | 1.00 | 0.77 | 0.45 | 1.10   | 1.10 | 0.85 | 0.50 |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.

# TWA-X Series with Extension to 230°C



## Wet Electrolytic Tantalum Capacitor

### CAPACITANCE AND RATED VOLTAGE, $V_R$ (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance   |      | Rated Voltage DC ( $V_R$ ) to 85°C |      |      |
|---------------|------|------------------------------------|------|------|
| $\mu\text{F}$ | Code | 75V                                | 100V | 125V |
| 220           | 227  |                                    |      |      |
| 330           | 337  |                                    |      | E    |
| 400           | 407  |                                    | E    |      |
| 470           | 477  |                                    |      |      |

Available Ratings

### RATINGS & PART NUMBER REFERENCE

| AVX Part Number     | Case Size |      | Cap ( $\mu\text{F}$ )<br>25°C at<br>120Hz | DC<br>Rated<br>Voltage<br>(V)<br>At 85°C | ESR<br>max<br>(Ohms)<br>at 120Hz | DC Leakage<br>max ( $\mu\text{A}$ ) |                    | Impedance<br>max<br>(Ohms)<br>-55°C<br>at 120 Hz | Maximum Capacitance<br>change (%) |       |        | AC<br>Ripple<br>(mA rms)<br>85°C<br>at<br>40kHz | 85°C<br>Capability<br>max.<br>Time at<br>85°C<br>(hrs) | 200°C Capability max. |                           |                                     | 230°C Capability max |                           |                                     |
|---------------------|-----------|------|---|--|----------------------------------|-------------------------------------|--------------------|--|-----------------------------------|-------|--------|---|--|-----------------------|---------------------------|-------------------------------------|----------------------|---------------------------|-------------------------------------|
|                     | AVX       | DSCC |   |  |                                  | +25°C                               | +85<br>&<br>+125°C |  | -55°C                             | +85°C | +125°C |   |  | $U_r$<br>(V)          | Time at<br>200°C<br>(hrs) | DCL @<br>200°C<br>( $\mu\text{A}$ ) | $U_r$<br>(V)         | Time at<br>230°C<br>(hrs) | DCL @<br>230°C<br>( $\mu\text{A}$ ) |
| TWAE407*100=BKZ0*00 | E         | T4   | 400                                       | 100                                      | 0.8                              | 10                                  | 150                | 10   | -50                               | 10    | 35     | 4100  | 2000   | 60                    | 2000                      | 1000                                | 25                   | 500                       | 1000                                |
| TWAE337*125=BKZ0*00 | E         | T4   | 330                                       | 125                                      | 0.8                              | 10                                  | 60                 | 10   | -45                               | 15    | 25     | 3600  | 500  | 75                    | 500                       | 1000                                | 40                   | 500                       | 1000                                |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.

DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

$$DF = 2\pi fC \times (\text{ESR})$$

$$2\pi = 6.28$$

$$f = 120\text{Hz}$$


C = Actual measured capacitance

ESR = Actual measured ESR

# TWS Electrolytic Tantalum Capacitor



## DSCC 13017



Operating Temperature -55°C to 125°C

The TWS series, built to the requirements of DSCC 13017, represents a family of axial leaded wet tantalum capacitors that encompasses the high capacitance values of DSCC 93026 with additional mechanical stability for increased vibration capability.

Vibration Capabilities:

Vibration: MIL-PRF-39006, MIL-STD-202, Method 204, Test Condition E, 50 g

Random Vibration: MIL-PRF-39006, MIL-STD-202, Method 214, Test condition II-G, 27.78 g


Shock: MIL-PRF-39006, MIL-STD-202, Method 213, Condition D, 500 g

Components built to DSCC 13017 also see enhanced thermal shock testing with an increase from the standard 30 cycles to 300 cycles.

In addition, this family includes reverse voltage testing in accordance with MIL-PRF-39006, with a maximum dc potential of -3 V.

Customized capacitance and voltage packages are possible and welcomed. Contact the factory about design possibilities beyond those contained in this datasheet.

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)


| DSCC Case Size | AVX Case Size | L                              | D  | D                             | E             |
|----------------|---------------|--------------------------------|--|-------------------------------|---------------|
|                |               | +0.79 (0.031)<br>-0.41 (0.016) | Without Insulating Sleeve<br>±0.41 (0.016) | With Insulating Sleeve<br>Max | ±6.35 (0.250) |
| T1             | A             | 11.51 (0.453)                  | 4.78 (0.188)                               | 5.56 (0.219)                  | 38.10 (1.500) |
| T2             | B             | 16.28 (0.641)                  | 7.14 (0.281)                               | 7.92 (0.312)                  | 57.15 (2.250) |
| T3             | D             | 19.46 (0.766)                  | 9.52 (0.375)                               | 10.31 (0.406)                 | 57.15 (2.250) |
| T4             | E             | 26.97 (1.062)                  | 9.52 (0.375)                               | 10.31 (0.406)                 | 57.15 (2.250) |

# TWS Electrolytic Tantalum Capacitor




## DSCC 13017


### HOW TO ORDER AVX PART NUMBER:



### DSCC PART IDENTIFICATION NUMBER (PIN):



### SPACE LEVEL OPTIONS TO SRW9000\*:



For RoHS compliant products, please select correct termination style.

Not RoHS Compliant

\*Check with factory for availability and testing details.

### RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/</sup>

| Frequency of Applied Ripple Current | 120Hz |      |      |      | 800Hz |      |      |      | 1kHz |      |      |      |   |
|-------------------------------------|-------|------|------|------|-------|------|------|------|------|------|------|------|---|
|                                     | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |   |
| Ambient Still Air Temperature (°C)  | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |   |
| % of Rated Peak Voltage             | 100%  | 0.60 | 0.39 | –    | –     | 0.71 | 0.43 | –    | –    | 0.72 | 0.45 | –    | – |
| 85°C                                | 90%   | 0.60 | 0.46 | –    | –     | 0.71 | 0.55 | –    | –    | 0.72 | 0.55 | –    | – |
| Rated Peak Voltage                  | 80%   | 0.60 | 0.52 | 0.35 | –     | 0.71 | 0.62 | 0.42 | –    | 0.72 | 0.62 | 0.42 | – |
| 70%                                 | 0.60  | 0.58 | 0.44 | –    | 0.71  | 0.69 | 0.52 | –    | 0.72 | 0.70 | 0.52 | –    |   |
| 66-2/3%                             | 0.60  | 0.60 | 0.46 | 0.27 | 0.71  | 0.71 | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |   |

| Frequency of Applied Ripple Current | 10kHz |      |      |      | 40kHz |      |      |      | 100kHz |      |      |      |   |
|-------------------------------------|-------|------|------|------|-------|------|------|------|--------|------|------|------|---|
|                                     | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |   |
| Ambient Still Air Temperature (°C)  | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |   |
| % of Rated Peak Voltage             | 100%  | 0.88 | 0.55 | –    | –     | 1.00 | 0.63 | –    | –      | 1.10 | 0.69 | –    | – |
| 85°C                                | 90%   | 0.88 | 0.67 | –    | –     | 1.00 | 0.77 | –    | –      | 1.10 | 0.85 | –    | – |
| Rated Peak Voltage                  | 80%   | 0.88 | 0.76 | 0.52 | –     | 1.00 | 0.87 | 0.59 | –      | 1.10 | 0.96 | 0.65 | – |
| 70%                                 | 0.88  | 0.85 | 0.64 | –    | 1.00  | 0.97 | 0.73 | –    | 1.10   | 1.07 | 0.80 | –    |   |
| 66-2/3%                             | 0.88  | 0.88 | 0.68 | 0.40 | 1.00  | 1.00 | 0.77 | 0.45 | 1.10   | 1.10 | 0.85 | 0.50 |   |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.





# TWS Electrolytic Tantalum Capacitor



## DSCC 13017

### RATINGS & PART NUMBER REFERENCE

| AVX Part Number                        | DSCC Part Number | Cap (µF) 25°C at 120Hz | DC Rated Voltage (V) at 85°C | ESR max (ohms) at 120Hz | DC Leakage max (µA) |                | Impedance max (Ohms) -55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms) 85°C at 40kHz | Case Size |      |
|--|------------------|------------------------|------------------------------|-------------------------|---------------------|----------------|-------------------------------------|--------------------------------|-------|--------|----------------------------------|-----------|------|
|  |                  |                        |                              |                         | +25°C               | +85°C & +125°C |                                     | -55°C                          | +85°C | +125°C |                                  | AVX       | DSCC |
| <b>25 VDC at 85°C 15 VDC at 125°C</b>  |                  |                        |                              |                         |                     |                |                                     |                                |       |        |                                  |           |      |
| TWSB567*025□B#Z0000                    | 13017-02*□       | 560                    | 25                           | 0.83                    | 2                   | 10             | 12                                  | -65                            | 14    | 18     | 2000                             | B         | T2   |
| TWSD128*025□B#Z0000                    | 13017-03*□       | 1200                   | 25                           | 0.65                    | 5                   | 20             | 7                                   | -70                            | 15    | 20     | 2400                             | D         | T3   |
| TWSE188*025□B#Z0000                    | 13017-04*□       | 1800                   | 25                           | 0.5                     | 6                   | 25             | 7                                   | -72                            | 15    | 20     | 3000                             | E         | T4   |
| <b>30 VDC at 85°C 20 VDC at 125°C</b>  |                  |                        |                              |                         |                     |                |                                     |                                |       |        |                                  |           |      |
| TWSB477*030□B#Z0000                    | 13017-06*□       | 470                    | 30                           | 0.85                    | 2                   | 10             | 15                                  | -65                            | 14    | 18     | 1800                             | B         | T2   |
| TWSD108*030□B#Z0000                    | 13017-07*□       | 1000                   | 30                           | 0.7                     | 7                   | 25             | 7                                   | -70                            | 15    | 25     | 2200                             | D         | T3   |
| TWSE158*030□B#Z0000                    | 13017-08*□       | 1500                   | 30                           | 0.6                     | 12                  | 35             | 6                                   | -72                            | 15    | 25     | 2900                             | E         | T4   |
| <b>50 VDC at 85°C 30 VDC at 125°C</b>  |                  |                        |                              |                         |                     |                |                                     |                                |       |        |                                  |           |      |
| TWSB227*050□B#Z0000                    | 13017-10*□       | 220                    | 50                           | 0.9                     | 2                   | 10             | 17.5                                | -50                            | 8     | 15     | 1800                             | B         | T2   |
| TWSE687*050□B#Z0000                    | 13017-12*□       | 680                    | 50                           | 0.7                     | 5                   | 40             | 8                                   | -58                            | 10    | 20     | 2700                             | E         | T4   |
| <b>60V VDC at 85°C 40 VDC at 125°C</b> |                  |                        |                              |                         |                     |                |                                     |                                |       |        |                                  |           |      |
| TWSB157*060□B#Z0000                    | 13017-14*□       | 150                    | 60                           | 1.1                     | 2                   | 10             | 20                                  | -40                            | 8     | 15     | 1800                             | B         | T2   |
| TWSE567*060□B#Z0000                    | 13017-16*□       | 560                    | 60                           | 0.8                     | 5                   | 40             | 10                                  | -58                            | 8     | 15     | 2700                             | E         | T4   |
| <b>75V VDC at 85°C 50 VDC at 125°C</b> |                  |                        |                              |                         |                     |                |                                     |                                |       |        |                                  |           |      |
| TWSA336*075□B#Z0000                    | 13017-17*□       | 33                     | 75                           | 2.5                     | 1                   | 5              | 66                                  | -25                            | 5     | 9      | 1050                             | A         | T1   |
| TWSB117*075□B#Z0000                    | 13017-18*□       | 110                    | 75                           | 1.3                     | 2                   | 10             | 24                                  | -35                            | 6     | 10     | 1650                             | B         | T2   |
| TWSE477*075□B#Z0000                    | 13017-20*□       | 470                    | 75                           | 0.9                     | 5                   | 50             | 12                                  | -50                            | 6     | 10     | 2700                             | E         | T4   |
| <b>100 VDC at 85°C 65 VDC at 125°C</b> |                  |                        |                              |                         |                     |                |                                     |                                |       |        |                                  |           |      |
| TWSA156*100□B#Z0000                    | 13017-21*□       | 15                     | 100                          | 3.5                     | 1                   | 5              | 125                                 | -18                            | 3     | 10     | 1050                             | A         | T1   |
| TWSB686*100□B#Z0000                    | 13017-22*□       | 68                     | 100                          | 2.1                     | 2                   | 10             | 37                                  | -30                            | 4     | 12     | 1650                             | B         | T2   |
| TWSE227*100□B#Z0000                    | 13017-24*□       | 220                    | 100                          | 1.2                     | 5                   | 50             | 15                                  | -40                            | 6     | 12     | 2700                             | E         | T4   |


All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum




This data sheet contains the MIL-PRF-39006 ratings for which AVX is a qualified approved supplier. This will be continually updated as the qualification expands. For COTS-Plus equivalent ratings please refer to the TWC data sheet located on the website.

This design is an axial leaded tubular case. It includes a welded tantalum can and header assembly that provides a hermetic seal to withstand harsh environments. The 1000 hour failure rates of 1%, 0.1% and 0.01% correspond to "M", "P", and "R" respectively. For details on testing conditions please refer to MIL-PRF-39006.

**Currently qualified M39006 ratings include T2-T4 case sizes:**

|           | M Level<br>Reliability Dashes | P Level<br>Reliability Dashes | R Level<br>Reliability Dashes |
|-----------|-------------------------------|-------------------------------|-------------------------------|
| M39006/22 | 6V-100V                       | 6V-100V                       | 6V-100V                       |
| M39006/25 | 6V-100V                       | 6V-100V                       | 6V-100V                       |
| M39006/30 | 6V-100V                       | 6V-100V                       | 6V-100V                       |
| M39006/31 | 6V-100V                       | 6V-100V                       | 6V-100V                       |

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)

| DSCC Case Size | AVX Case Size | L                              | D                           | D                     | E             |
|----------------|---------------|--------------------------------|-----------------------------|-----------------------|---------------|
|                |               | +0.79 (0.031)<br>-0.41 (0.016) | Basic Case<br>±0.41 (0.016) | Insulated Case<br>Max | ±6.35 (0.250) |
| T1             | A             | 11.51 (0.453)                  | 4.78 (0.188)                | 5.56 (0.219)          | 38.10 (1.500) |
| T2             | B             | 16.28 (0.641)                  | 7.14 (0.281)                | 7.92 (0.312)          | 57.15 (2.250) |
| T3             | D             | 19.46 (0.766)                  | 9.52 (0.375)                | 10.31 (0.406)         | 57.15 (2.250) |
| T4             | E             | 26.97 (1.062)                  | 9.52 (0.375)                | 10.31 (0.406)         | 57.15 (2.250) |

### VOLTAGE RATINGS (Operating Temperature -55°C to 125°C)

| Voltage (DC)               |       |     |     |      |      |      |      |      |    |      |     |     |
|----------------------------|-------|-----|-----|------|------|------|------|------|----|------|-----|-----|
| Rated Voltage: ( $V_r$ )   | 85°C  | 6   | 8   | 10   | 15   | 25   | 30   | 50   | 60 | 75   | 100 | 125 |
| Derated Voltage: ( $V_c$ ) | 125°C | 4   | 5   | 6    | 10   | 15   | 20   | 30   | 40 | 50   | 65  | 85  |
| Surge Voltage: ( $V_s$ )   | 85°C  | 6.9 | 9.2 | 11.5 | 17.3 | 28.8 | 34.5 | 57.5 | 69 | 86.3 | 115 | 144 |




# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum

### HOW TO ORDER MILITARY M39006 PART NUMBER:



\*High vibration qualified parts are currently under development. Please contact the factory for additional details and availability.

### RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/3/</sup>

| Frequency of Applied Ripple Current |         | 120Hz |      |      |      | 800Hz |      |      |      | 1kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |
| Ambient Still Air Temperature (°C)  |         |       |      |      |      |       |      |      |      |      |      |      |      |
| % of                                | 100%    | 0.60  | 0.39 | –    | –    | 0.71  | 0.43 | –    | –    | 0.72 | 0.45 | –    | –    |
| 85°C                                | 90%     | 0.60  | 0.46 | –    | –    | 0.71  | 0.55 | –    | –    | 0.72 | 0.55 | –    | –    |
| Rated                               | 80%     | 0.60  | 0.52 | 0.35 | –    | 0.71  | 0.62 | 0.42 | –    | 0.72 | 0.62 | 0.42 | –    |
| Peak                                | 70%     | 0.60  | 0.58 | 0.44 | –    | 0.71  | 0.69 | 0.52 | –    | 0.72 | 0.70 | 0.52 | –    |
| Voltage                             | 66-2/3% | 0.60  | 0.60 | 0.46 | 0.27 | 0.71  | 0.71 | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |

| Frequency of Applied Ripple Current |         | 10kHz |      |      |      | 40kHz |      |      |      | 100kHz |      |      |      |
|-------------------------------------|---------|-------|------|------|------|-------|------|------|------|--------|------|------|------|
|                                     |         | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |
| Ambient Still Air Temperature (°C)  |         |       |      |      |      |       |      |      |      |        |      |      |      |
| % of                                | 100%    | 0.88  | 0.55 | –    | –    | 1.00  | 0.63 | –    | –    | 1.10   | 0.69 | –    | –    |
| 85°C                                | 90%     | 0.88  | 0.67 | –    | –    | 1.00  | 0.77 | –    | –    | 1.10   | 0.85 | –    | –    |
| Rated                               | 80%     | 0.88  | 0.76 | 0.52 | –    | 1.00  | 0.87 | 0.59 | –    | 1.10   | 0.96 | 0.65 | –    |
| Peak                                | 70%     | 0.88  | 0.85 | 0.64 | –    | 1.00  | 0.97 | 0.73 | –    | 1.10   | 1.07 | 0.80 | –    |
| Voltage                             | 66-2/3% | 0.88  | 0.88 | 0.68 | 0.40 | 1.00  | 1.00 | 0.77 | 0.45 | 1.10   | 1.10 | 0.85 | 0.50 |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.

3/ The ripple current listed in the parametric tables represents a rating calculated by using a maximum internal temperature rise (ΔT) at 50°C at 40 kHz at 85°C ambient temperature, with a maximum peak rated voltage of 66.67 percent of the 85°C peak voltage rating.



# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum

### M39006 /22 RATINGS AND DASH NUMBER REFERENCE

| M39006/22 Dashes |         |         | Tolerance ± (%) | Cap (µF) 25°C at 120Hz | DC Rated Voltage (V) at 85°C | DC Leakage (µA) |                | DF max (%) | ESR max (Ohms) at 120Hz | Impedance max (Ohms) -55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms) 85°C at 40kHz | Case Size |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
|------------------|---------|---------|-----------------|------------------------|------------------------------|-----------------|----------------|------------|-------------------------|-------------------------------------|--------------------------------|-------|--------|----------------------------------|-----------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|-------|-------|-------|----|----|
| M Level          | P Level | R Level |                 |                        |                              | +25°C           | +85°C & +125°C |            |                         |                                     | -55°C                          | +85°C | +125°C |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0007            | -0227   | -0447   | 20              | 140                    | 6                            | 1               | 3              | 21         | 1.99                    | 40                                  | -40                            | 14    | 16     | 1200                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0008            | -0228   | -0448   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0009            | -0229   | -0449   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0010            | -0230   | -0450   | 20              | 270                    | 6                            | 1               | 6.5            | 45         | 2.21                    | 25                                  | -44                            | 17.5  | 20     | 1375                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0011            | -0231   | -0451   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0012            | -0232   | -0452   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0013            | -0233   | -0453   | 20              | 330                    | 6                            | 2               | 7.9            | 36         | 1.45                    | 20                                  | -44                            | 14    | 16     | 1800                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0014            | -0234   | -0454   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0015            | -0235   | -0455   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0016            | -0236   | -0456   | 20              | 560                    | 6                            | 2               | 13             | 55         | 1.3                     | 25                                  | -64                            | 17.5  | 20     | 1900                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0017            | -0237   | -0457   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0018            | -0238   | -0458   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0019            | -0239   | -0459   | 20              | 1200                   | 6                            | 3               | 14             | 90         | 1                       | 20                                  | -80                            | 25    | 25     | 2265                             | T4        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0020            | -0240   | -0460   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0021            | -0241   | -0461   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0022            | -0242   | -0462   | 20              | 120                    | 8                            | 1               | 2              | 20         | 2.21                    | 50                                  | -44                            | 17.5  | 20     | 1220                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0023            | -0243   | -0463   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0024            | -0244   | -0464   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0025            | -0245   | -0465   | 20              | 220                    | 8                            | 1               | 7              | 37         | 2.23                    | 30                                  | -44                            | 17.5  | 20     | 1370                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0026            | -0246   | -0466   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0027            | -0247   | -0467   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0028            | -0248   | -0468   | 20              | 290                    | 8                            | 2               | 6              | 34         | 1.56                    | 25                                  | -64                            | 17.5  | 20     | 1770                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0029            | -0249   | -0469   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0030            | -0250   | -0470   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0031            | -0251   | -0471   | 20              | 430                    | 8                            | 2               | 14             | 46         | 1.42                    | 25                                  | -64                            | 17.5  | 20     | 1825                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0032            | -0252   | -0472   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0033            | -0253   | -0473   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0034            | -0254   | -0474   | 20              | 850                    | 8                            | 4               | 16             | 60         | 0.94                    | 22                                  | -80                            | 25    | 25     | 2330                             | T4        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0035            | -0255   | -0475   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0036            | -0256   | -0476   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0037            | -0257   | -0477   | 20              | 100                    | 10                           | 1               | 4              | 15         | 1.99                    | 60                                  | -36                            | 14    | 16     | 1200                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0038            | -0258   | -0478   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0039            | -0259   | -0479   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0040            | -0260   | -0480   | 20              | 180                    | 10                           | 1               | 7              | 30         | 2.21                    | 40                                  | -36                            | 14    | 16     | 1.365                            | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0041            | -0261   | -0481   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0042            | -0262   | -0482   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0043            | -0263   | -0483   | 20              | 250                    | 10                           | 2               | 10             | 30         | 1.59                    | 30                                  | -40                            | 14    | 16     | 1720                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0044            | -0264   | -0484   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0045            | -0265   | -0485   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0046            | -0266   | -0486   | 20              | 390                    | 10                           | 2               | 16             | 44         | 1.5                     | 25                                  | -64                            | 17.5  | 20     | 1800                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0047            | -0267   | -0487   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0048            | -0268   | -0488   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0049            | -0269   | -0489   | 20              | 750                    | 10                           | 4               | 16             | 50         | 0.88                    | 23                                  | -80                            | 25    | 25     | 2360                             | T4        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0050            | -0270   | -0490   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0051            | -0271   | -0491   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0052            | -0272   | -0492   | 20              | 70                     | 15                           | 1               | 4              | 13         | 2.46                    | 75                                  | -28                            | 14    | 16     | 1150                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0053            | -0273   | -0493   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0054            | -0274   | -0494   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0055            | -0275   | -0495   | 20              | 120                    | 15                           | 1               | 7              | 18         | 1.99                    | 50                                  | -28                            | 17.5  | 20     | 1450                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0056            | -0276   | -0496   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0057            | -0277   | -0497   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0058            | -0278   | -0498   | 20              | 170                    | 15                           | 2               | 10             | 25         | 1.95                    | 35                                  | -32                            | 14    | 16     | 1480                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0059            | -0279   | -0499   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0060            | -0280   | -0500   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0061            | -0281   | -0501   | 20              | 270                    | 15                           | 2               | 16             | 32         | 1.57                    | 30                                  | -56                            | 17.5  | 20     | 1740                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0062            | -0282   | -0502   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0063            | -0283   | -0503   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0064            | -0284   | -0504   | 20              | 540                    | 15                           | 6               | 24             | 40         | 0.98                    | 23                                  | -80                            | 25    | 25     | 2330                             | T4        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0065            | -0285   | -0505   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0066            | -0286   | -0506   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0067            | -0287   | -0507   | 20              | 50                     | 25                           | 1               | 2              | 11         | 2.92                    | 70                                  | -28                            | 13    | 15     | 1130                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0068            | -0288   | -0508   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0069            | -0289   | -0509   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0070            | -0290   | -0510   | 20              | 100                    | 25                           | 1               | 10             | 15         | 1.99                    | 50                                  | -28                            | 13    | 15     | 1435                             | T2        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0071            | -0291   | -0511   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0072            | -0292   | -0512   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0073            | -0293   | -0513   | 20              | 120                    | 25                           | 2               | 6              | 21         | 2.32                    | 38                                  | -32                            | 13    | 15     | 1450                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0074            | -0294   | -0514   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0075            | -0295   | -0515   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0076            | -0296   | -0516   | 20              | 180                    | 25                           | 2               | 18             | 26         | 1.92                    | 32                                  | -48                            | 13    | 15     | 1525                             | T3        |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0077            | -0297   | -0517   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0078            | -0298   | -0518   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |       |       |       |    |    |
| -0079            | -0299   | -0519   | 20              | -0080                  | -0300                        | -0520           | 10             | 20         | -0081                   | -0301                               | -0521                          | 10    | 20     | -0082                            | -0302     | -0522 | 10 | 20 | -0083 | -0303 | -0523 | 10 | 20 | -0084 | -0304 | -0524 | 10 | 20 | -0085 | -0305 | -0525 | 10 | 20 | -0086 | -0306 | -0526 | 10 | 20 | -0087 | -0307 | -0527 | 10 | 20 | -0088 | -0308 | -0528 | 10 | 20 | -0089 | -0309 | -0529 | 10 | 20 | -0090 | -0310 | -0530 | 10 | 20 | -0091 | -0311 | -0531 | 10 | 20 | -0092 | -0312 | -0532 | 10 | 20 | -0093 | -0313 | -0533 | 10 | 20 | -0094 | -0314 | -0534 | 10 | 20 | -0095 | -0315 | -0535 | 10 | 20 | -0096 | -0316 | -0536 | 10 | 20 | -0097 | -0317 | -0537 | 10 | 20 | -0098 | -0318 | -0538 | 10 | 20 |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.



# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum

| M39006/22 Dashes |         |         | Tolerance ± (%) | Cap (µF) 25°C at 120Hz | DC Rated Voltage (V) at 85°C | DC Leakage (µA) |                | DF max (%) | ESR max (Ohms) at 120Hz | Impedance max (Ohms) -55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms) 85°C at 40kHz | Case Size |
|------------------|---------|---------|-----------------|------------------------|------------------------------|-----------------|----------------|------------|-------------------------|-------------------------------------|--------------------------------|-------|--------|----------------------------------|-----------|
| M Level          | P Level | R Level |                 |                        |                              | +25°C           | +85°C & +125°C |            |                         |                                     | -55°C                          | +85°C | +125°C |                                  |           |
| -0099            | -0319   | -0539   | 20              | 350                    | 25                           | 7               | 28             | 35         | 1.33                    | 24                                  | -70                            | 25    | 25     | 1970                             | T4        |
| -0100            | -0320   | -0540   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0107            | -0327   | -0547   | 20              | 40                     | 30                           | 1               | 5              | 10         | 3.32                    | 65                                  | -24                            | 10.5  | 12     | 1120                             | T2        |
| -0108            | -0328   | -0548   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0109            | -0329   | -0549   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0110            | -0330   | -0550   | 20              | 68                     | 30                           | 1               | 8              | 13         | 2.54                    | 60                                  | -24                            | 13    | 15     | 1285                             | T2        |
| -0111            | -0331   | -0551   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0112            | -0332   | -0552   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0113            | -0333   | -0553   | 20              | 100                    | 30                           | 2               | 12             | 17         | 2.26                    | 40                                  | -28                            | 10.5  | 12     | 1450                             | T3        |
| -0114            | -0334   | -0554   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0115            | -0335   | -0555   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0116            | -0336   | -0556   | 20              | 150                    | 30                           | 2               | 18             | 23         | 2.03                    | 35                                  | -48                            | 13    | 15     | 1525                             | T3        |
| -0117            | -0337   | -0557   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0118            | -0338   | -0558   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0119            | -0339   | -0559   | 20              | 300                    | 30                           | 8               | 32             | 31         | 1.37                    | 25                                  | -60                            | 25    | 25     | 1950                             | T4        |
| -0120            | -0340   | -0560   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0127            | -0347   | -0567   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0128            | -0348   | -0568   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0129            | -0349   | -0569   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0130            | -0350   | -0570   | 20              | 47                     | 50                           | 1               | 9              | 11         | 3.11                    | 70                                  | -28                            | 13    | 15     | 1155                             | T2        |
| -0131            | -0351   | -0571   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0132            | -0352   | -0572   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0133            | -0353   | -0573   | 20              | 60                     | 50                           | 2               | 12             | 12         | 2.65                    | 45                                  | -16                            | 10.5  | 12     | 1335                             | T3        |
| -0134            | -0354   | -0574   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0135            | -0355   | -0575   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0136            | -0356   | -0576   | 20              | 82                     | 50                           | 2               | 16             | 15         | 2.43                    | 45                                  | -32                            | 13    | 15     | 1400                             | T3        |
| -0137            | -0357   | -0577   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0138            | -0358   | -0578   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0139            | -0359   | -0579   | 20              | 160                    | 50                           | 8               | 32             | 17         | 1.41                    | 27                                  | -50                            | 25    | 25     | 1900                             | T4        |
| -0140            | -0360   | -0580   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0147            | -0367   | -0587   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0148            | -0368   | -0588   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0149            | -0369   | -0589   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0150            | -0370   | -0590   | 20              | 39                     | 60                           | 1               | 9              | 10         | 3.4                     | 90                                  | -28                            | 10.5  | 12     | 1110                             | T2        |
| -0151            | -0371   | -0591   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0152            | -0372   | -0592   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0153            | -0373   | -0593   | 20              | 50                     | 60                           | 2               | 12             | 10         | 2.65                    | 50                                  | -16                            | 10.5  | 12     | 1330                             | T3        |
| -0154            | -0374   | -0594   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0155            | -0375   | -0595   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0156            | -0376   | -0596   | 20              | 68                     | 60                           | 2               | 16             | 13         | 2.54                    | 50                                  | -32                            | 10.5  | 12     | 1365                             | T3        |
| -0157            | -0377   | -0597   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0158            | -0378   | -0598   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0159            | -0379   | -0599   | 20              | 140                    | 60                           | 8               | 32             | 16         | 1.52                    | 28                                  | -40                            | 20    | 20     | 1850                             | T4        |
| -0160            | -0380   | -0600   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0167            | -0387   | -0607   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0168            | -0388   | -0608   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0169            | -0389   | -0609   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0170            | -0390   | -0610   | 20              | 33                     | 75                           | 1               | 10             | 10         | 4.02                    | 90                                  | -24                            | 10.5  | 15     | 1000                             | T2        |
| -0171            | -0391   | -0611   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0172            | -0392   | -0612   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0173            | -0393   | -0613   | 20              | 40                     | 75                           | 2               | 12             | 9          | 2.99                    | 60                                  | -16                            | 10.5  | 12     | 1250                             | T3        |
| -0174            | -0394   | -0614   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0175            | -0395   | -0615   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0176            | -0396   | -0616   | 20              | 56                     | 75                           | 2               | 17             | 11         | 2.61                    | 60                                  | -28                            | 10.5  | 15     | 1335                             | T3        |
| -0177            | -0397   | -0617   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0178            | -0398   | -0618   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0179            | -0399   | -0619   | 20              | 110                    | 75                           | 9               | 36             | 12         | 1.45                    | 29                                  | -35                            | 20    | 20     | 1850                             | T4        |
| -0180            | -0400   | -0620   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0187            | -0407   | -0627   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0188            | -0408   | -0628   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0189            | -0409   | -0629   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0190            | -0410   | -0630   | 20              | 22                     | 100                          | 1               | 9              | 7.5        | 4.52                    | 100                                 | -16                            | 8     | 8      | 965                              | T2        |
| -0191            | -0411   | -0631   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0192            | -0412   | -0632   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0193            | -0413   | -0633   | 20              | 30                     | 100                          | 2               | 12             | 7          | 3.1                     | 80                                  | -16                            | 8     | 8      | 1240                             | T3        |
| -0194            | -0414   | -0634   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0195            | -0415   | -0635   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0196            | -0416   | -0636   | 20              | 43                     | 100                          | 2               | 17             | 8.5        | 2.62                    | 70                                  | -20                            | 8     | 8      | 1335                             | T3        |
| -0197            | -0417   | -0637   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0198            | -0418   | -0638   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0199            | -0419   | -0639   | 20              | 86                     | 100                          | 9               | 36             | 10         | 1.54                    | 30                                  | -25                            | 15    | 15     | 1800                             | T4        |
| -0200            | -0420   | -0640   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.



# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum

### M39006/25 RATINGS AND DASH NUMBER REFERENCE

| M39006/25 Dashes |         |         | Tolerance ± (%) | Cap (µF) 25°C at 120Hz | DC Rated Voltage (V) at 85°C | DC Leakage (µA) |                | DF max (%) | ESR max (Ohms) at 120Hz | Impedance max (Ohms) -55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms) 85°C at 40kHz | Case Size |
|------------------|---------|---------|-----------------|------------------------|------------------------------|-----------------|----------------|------------|-------------------------|-------------------------------------|--------------------------------|-------|--------|----------------------------------|-----------|
| M Level          | P Level | R Level |                 |                        |                              | +25°C           | +85°C & +125°C |            |                         |                                     | -55°C                          | +85°C | +125°C |                                  |           |
| -0003            | -0091   | -0179   | 20              | 820                    | 6                            | 3               | 14             | 155        | 2.51                    | 18                                  | -88                            | 16    | 20     | 1500                             | T2        |
| -0004            | -0092   | -0180   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0005            | -0093   | -0181   | 20              | 1500                   | 6                            | 5               | 20             | 172        | 1.52                    | 18                                  | -90                            | 20    | 25     | 1900                             | T3        |
| -0006            | -0094   | -0182   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0007            | -0095   | -0183   | 20              | 2200                   | 6                            | 6               | 24             | 170        | 1.03                    | 13                                  | -90                            | 25    | 30     | 2300                             | T4        |
| -0008            | -0096   | -0184   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0011            | -0099   | -0187   | 20              | 680                    | 8                            | 3               | 14             | 130        | 2.54                    | 22                                  | -83                            | 16    | 20     | 1500                             | T2        |
| -0012            | -0100   | -0188   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0013            | -0101   | -0189   | 20              | 1500                   | 8                            | 5               | 20             | 170        | 1.5                     | 18                                  | -90                            | 20    | 25     | 1900                             | T3        |
| -0014            | -0102   | -0190   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0015            | -0103   | -0191   | 20              | 1800                   | 8                            | 7               | 25             | 138        | 1.02                    | 14                                  | -90                            | 25    | 30     | 2300                             | T4        |
| -0016            | -0104   | -0192   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0019            | -0107   | -0195   | 20              | 560                    | 10                           | 3               | 16             | 106        | 2.51                    | 27                                  | -77                            | 16    | 20     | 1450                             | T2        |
| -0020            | -0108   | -0196   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0021            | -0109   | -0197   | 20              | 1200                   | 10                           | 5               | 20             | 137        | 1.51                    | 18                                  | -88                            | 20    | 25     | 1850                             | T3        |
| -0022            | -0110   | -0198   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0023            | -0111   | -0199   | 20              | 1500                   | 10                           | 7               | 25             | 114        | 1.01                    | 15                                  | -88                            | 25    | 30     | 2300                             | T4        |
| -0024            | -0112   | -0200   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0027            | -0115   | -0203   | 20              | 390                    | 15                           | 3               | 16             | 74         | 2.52                    | 31                                  | -66                            | 16    | 20     | 1450                             | T2        |
| -0028            | -0116   | -0204   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0029            | -0117   | -0205   | 20              | 820                    | 15                           | 6               | 24             | 111        | 1.8                     | 22                                  | -77                            | 20    | 25     | 1800                             | T3        |
| -0030            | -0118   | -0206   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0031            | -0119   | -0207   | 20              | 1000                   | 15                           | 8               | 32             | 92         | 1.22                    | 17                                  | -77                            | 25    | 30     | 2300                             | T4        |
| -0032            | -0120   | -0208   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0035            | -0123   | -0211   | 20              | 270                    | 25                           | 3               | 16             | 55         | 2.7                     | 33                                  | -62                            | 13    | 16     | 1400                             | T2        |
| -0036            | -0124   | -0212   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0037            | -0125   | -0213   | 20              | 560                    | 25                           | 7               | 28             | 76         | 1.8                     | 24                                  | -72                            | 20    | 25     | 1750                             | T3        |
| -0038            | -0126   | -0214   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0039            | -0127   | -0215   | 20              | 680                    | 25                           | 8               | 32             | 63         | 1.23                    | 19                                  | -72                            | 25    | 30     | 2100                             | T4        |
| -0040            | -0128   | -0216   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0043            | -0131   | -0219   | 20              | 220                    | 30                           | 3               | 16             | 42         | 2.53                    | 36                                  | -60                            | 13    | 16     | 1200                             | T2        |
| -0044            | -0132   | -0220   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0045            | -0133   | -0221   | 20              | 470                    | 30                           | 8               | 32             | 64         | 1.81                    | 25                                  | -65                            | 20    | 25     | 1500                             | T3        |
| -0046            | -0134   | -0222   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0047            | -0135   | -0223   | 20              | 560                    | 30                           | 9               | 36             | 55         | 1.3                     | 20                                  | -65                            | 25    | 30     | 2000                             | T4        |
| -0048            | -0136   | -0224   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0051            | -0139   | -0227   | 20              | 120                    | 50                           | 4               | 24             | 22.5       | 2.49                    | 49                                  | -42                            | 12    | 15     | 1200                             | T2        |
| -0052            | -0140   | -0228   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0053            | -0141   | -0229   | 20              | 270                    | 50                           | 8               | 32             | 37         | 1.82                    | 29                                  | -46                            | 20    | 25     | 1450                             | T3        |
| -0054            | -0142   | -0230   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0055            | -0143   | -0231   | 20              | 330                    | 50                           | 9               | 36             | 38         | 1.53                    | 22                                  | -46                            | 25    | 30     | 1900                             | T4        |
| -0056            | -0144   | -0232   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0059            | -0147   | -0235   | 20              | 100                    | 60                           | 4               | 20             | 19         | 2.52                    | 54                                  | -36                            | 12    | 15     | 1100                             | T2        |
| -0060            | -0148   | -0236   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0061            | -0149   | -0237   | 20              | 220                    | 60                           | 8               | 32             | 30         | 1.81                    | 29                                  | -40                            | 16    | 20     | 1400                             | T3        |
| -0062            | -0150   | -0238   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0063            | -0151   | -0239   | 20              | 270                    | 60                           | 9               | 36             | 27         | 1.33                    | 23                                  | -45                            | 20    | 25     | 1850                             | T4        |
| -0064            | -0152   | -0240   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0067            | -0155   | -0243   | 20              | 82                     | 75                           | 4               | 24             | 15.2       | 2.46                    | 63                                  | -30                            | 12    | 15     | 1000                             | T2        |
| -0068            | -0156   | -0244   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0069            | -0157   | -0245   | 20              | 180                    | 75                           | 9               | 36             | 24.4       | 2.23                    | 30                                  | -35                            | 16    | 20     | 1300                             | T3        |
| -0070            | -0158   | -0246   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0071            | -0159   | -0247   | 20              | 220                    | 75                           | 10              | 40             | 37         | 1.8                     | 24                                  | -40                            | 20    | 25     | 1800                             | T4        |
| -0072            | -0160   | -0248   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0075            | -0163   | -0251   | 20              | 39                     | 100                          | 5               | 24             | 10.4       | 3.54                    | 80                                  | -20                            | 12    | 15     | 1300                             | T2        |
| -0076            | -0164   | -0252   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0077            | -0165   | -0253   | 20              | 68                     | 100                          | 10              | 40             | 11.3       | 2.21                    | 40                                  | -30                            | 14    | 16     | 1600                             | T3        |
| -0078            | -0166   | -0254   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0079            | -0167   | -0255   | 20              | 120                    | 100                          | 12              | 48             | 25         | 2.76                    | 30                                  | -35                            | 15    | 17     | 2000                             | T4        |
| -0080            | -0168   | -0256   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum

### M39006 /30 RATINGS AND DASH NUMBER REFERENCE

| M39006/30 Dashes |         |         | Tolerance ± (%) | Cap (µF) 25°C at 120Hz | DC Rated Voltage (V) at 85°C | DC Leakage (µA) |                | DF max (%) | ESR max (Ohms) at 120Hz | Impedance max (Ohms) -55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms) 85°C at 40kHz | Case Size |
|------------------|---------|---------|-----------------|------------------------|------------------------------|-----------------|----------------|------------|-------------------------|-------------------------------------|--------------------------------|-------|--------|----------------------------------|-----------|
| M Level          | P Level | R Level |                 |                        |                              | +25°C           | +85°C & +125°C |            |                         |                                     | -55°C                          | +85°C | +125°C |                                  |           |
| -0007            | -0227   | -0447   | 20              | 140                    | 6                            | 1               | 3              | 10.5       | 0.99                    | 40                                  | -40                            | 14    | 16     | 1200                             | T2        |
| -0008            | -0228   | -0448   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0009            | -0229   | -0449   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0010            | -0230   | -0450   | 20              | 270                    | 6                            | 1               | 6.5            | 22.5       | 1.11                    | 25                                  | -44                            | 17.5  | 20     | 1375                             | T2        |
| -0011            | -0231   | -0451   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0012            | -0232   | -0452   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0013            | -0233   | -0453   | 20              | 330                    | 6                            | 2               | 7.9            | 18         | 0.73                    | 20                                  | -44                            | 14    | 16     | 1800                             | T3        |
| -0014            | -0234   | -0454   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0015            | -0235   | -0455   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0016            | -0236   | -0456   | 20              | 560                    | 6                            | 2               | 13             | 27.5       | 0.65                    | 25                                  | -64                            | 17.5  | 20     | 1900                             | T3        |
| -0017            | -0237   | -0457   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0018            | -0238   | -0458   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0019            | -0239   | -0459   | 20              | 1200                   | 6                            | 3               | 14             | 45         | 0.5                     | 20                                  | -80                            | 25    | 25     | 2265                             | T4        |
| -0020            | -0240   | -0460   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0027            | -0247   | -0467   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0028            | -0248   | -0468   | 10              | 120                    | 8                            | 1               | 2              | 10         | 1.11                    | 50                                  | -44                            | 17.5  | 20     | 1220                             | T2        |
| -0029            | -0249   | -0469   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0030            | -0250   | -0470   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0031            | -0251   | -0471   | 10              | 220                    | 8                            | 1               | 7              | 18.5       | 1.12                    | 30                                  | -44                            | 17.5  | 20     | 1370                             | T2        |
| -0032            | -0252   | -0472   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0033            | -0253   | -0473   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0034            | -0254   | -0474   | 10              | 290                    | 8                            | 2               | 6              | 17         | 0.78                    | 25                                  | -64                            | 17.5  | 20     | 1770                             | T3        |
| -0035            | -0255   | -0475   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0036            | -0256   | -0476   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0037            | -0257   | -0477   | 10              | 430                    | 8                            | 2               | 14             | 23         | 0.71                    | 25                                  | -64                            | 17.5  | 20     | 1825                             | T3        |
| -0038            | -0258   | -0478   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0039            | -0259   | -0479   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0040            | -0260   | -0480   | 10              | 850                    | 8                            | 4               | 16             | 30         | 0.47                    | 22                                  | -80                            | 25    | 25     | 2330                             | T4        |
| -0047            | -0267   | -0487   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0048            | -0268   | -0488   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0049            | -0269   | -0489   | 5               | 100                    | 10                           | 1               | 4              | 7.5        | 0.99                    | 60                                  | -36                            | 14    | 16     | 1200                             | T2        |
| -0050            | -0270   | -0490   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0051            | -0271   | -0491   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0052            | -0272   | -0492   | 5               | 180                    | 10                           | 1               | 7              | 15         | 1.11                    | 40                                  | -36                            | 14    | 16     | 1.365                            | T2        |
| -0053            | -0273   | -0493   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0054            | -0274   | -0494   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0055            | -0275   | -0495   | 5               | 250                    | 10                           | 2               | 10             | 15         | 0.8                     | 30                                  | -40                            | 14    | 16     | 1720                             | T3        |
| -0056            | -0276   | -0496   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0057            | -0277   | -0497   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0058            | -0278   | -0498   | 5               | 390                    | 10                           | 2               | 16             | 22         | 0.75                    | 25                                  | -64                            | 17.5  | 20     | 1800                             | T3        |
| -0059            | -0279   | -0499   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0060            | -0280   | -0500   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0067            | -0287   | -0507   | 20              | 750                    | 10                           | 4               | 16             | 25         | 0.44                    | 23                                  | -80                            | 25    | 25     | 2360                             | T4        |
| -0068            | -0288   | -0508   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0069            | -0289   | -0509   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0070            | -0290   | -0510   | 20              | 70                     | 15                           | 1               | 4              | 6.5        | 1.23                    | 75                                  | -28                            | 14    | 16     | 1150                             | T2        |
| -0071            | -0291   | -0511   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0072            | -0292   | -0512   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0073            | -0293   | -0513   | 20              | 120                    | 15                           | 1               | 7              | 9          | 0.99                    | 50                                  | -28                            | 17.5  | 20     | 1450                             | T2        |
| -0074            | -0294   | -0514   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0075            | -0295   | -0515   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0076            | -0296   | -0516   | 20              | 170                    | 15                           | 2               | 10             | 12.5       | 0.98                    | 35                                  | -32                            | 14    | 16     | 1480                             | T3        |
| -0077            | -0297   | -0517   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0078            | -0298   | -0518   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0079            | -0299   | -0519   | 20              | 270                    | 15                           | 2               | 16             | 16         | 0.79                    | 30                                  | -56                            | 17.5  | 20     | 1740                             | T3        |
| -0080            | -0300   | -0520   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0087            | -0307   | -0527   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0088            | -0308   | -0528   | 10              | 540                    | 15                           | 6               | 24             | 20         | 0.49                    | 23                                  | -80                            | 25    | 25     | 2330                             | T4        |
| -0089            | -0309   | -0529   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0090            | -0310   | -0530   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0091            | -0311   | -0531   | 10              | 50                     | 25                           | 1               | 2              | 5.5        | 1.46                    | 70                                  | -28                            | 13    | 15     | 1130                             | T2        |
| -0092            | -0312   | -0532   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0093            | -0313   | -0533   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0094            | -0314   | -0534   | 10              | 100                    | 25                           | 1               | 10             | 7.5        | 0.99                    | 50                                  | -28                            | 13    | 15     | 1435                             | T2        |
| -0095            | -0315   | -0535   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0096            | -0316   | -0536   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0097            | -0317   | -0537   | 10              | 120                    | 25                           | 2               | 6              | 10.5       | 1.16                    | 38                                  | -32                            | 13    | 15     | 1450                             | T3        |
| -0098            | -0318   | -0538   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.



# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum

| M39006/30 Dashes |         |         | Tolerance ± (%) | Cap (µF) 25°C at 120Hz | DC Rated Voltage (V) at 85°C | DC Leakage (µA) |                | DF max (%) | ESR max (Ohms) at 120Hz | Impedance max (Ohms) -55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms) 85°C at 40kHz | Case Size |
|------------------|---------|---------|-----------------|------------------------|------------------------------|-----------------|----------------|------------|-------------------------|-------------------------------------|--------------------------------|-------|--------|----------------------------------|-----------|
| M Level          | P Level | R Level |                 |                        |                              | +25°C           | +85°C & +125°C |            |                         |                                     | -55°C                          | +85°C | +125°C |                                  |           |
| -0099            | -0319   | -0539   | 20              | 350                    | 25                           | 7               | 28             | 17.5       | 0.67                    | 24                                  | -70                            | 25    | 25     | 1970                             | T4        |
| -0100            | -0320   | -0540   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0107            | -0327   | -0547   | 20              | 40                     | 30                           | 1               | 5              | 5          | 1.66                    | 65                                  | -24                            | 10.5  | 12     | 1120                             | T2        |
| -0108            | -0328   | -0548   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0109            | -0329   | -0549   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0110            | -0330   | -0550   | 20              | 68                     | 30                           | 1               | 8              | 6.5        | 1.27                    | 60                                  | -24                            | 13    | 15     | 1285                             | T2        |
| -0111            | -0331   | -0551   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0112            | -0332   | -0552   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0113            | -0333   | -0553   | 20              | 100                    | 30                           | 2               | 12             | 8.5        | 1.13                    | 40                                  | -28                            | 10.5  | 12     | 1450                             | T3        |
| -0114            | -0334   | -0554   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0115            | -0335   | -0555   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0116            | -0336   | -0556   | 20              | 150                    | 30                           | 2               | 18             | 11.5       | 1.02                    | 35                                  | -48                            | 13    | 15     | 1525                             | T3        |
| -0117            | -0337   | -0557   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0118            | -0338   | -0558   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0119            | -0339   | -0559   | 20              | 300                    | 30                           | 8               | 32             | 15.5       | 0.69                    | 25                                  | -60                            | 25    | 25     | 1950                             | T4        |
| -0120            | -0340   | -0560   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0127            | -0347   | -0567   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0128            | -0348   | -0568   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0129            | -0349   | -0569   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0130            | -0350   | -0570   | 20              | 47                     | 50                           | 1               | 9              | 5.5        | 1.56                    | 70                                  | -28                            | 13    | 15     | 1155                             | T2        |
| -0131            | -0351   | -0571   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0132            | -0352   | -0572   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0133            | -0353   | -0573   | 20              | 60                     | 50                           | 2               | 12             | 6          | 1.33                    | 45                                  | -16                            | 10.5  | 12     | 1335                             | T3        |
| -0134            | -0354   | -0574   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0135            | -0355   | -0575   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0136            | -0356   | -0576   | 20              | 82                     | 50                           | 2               | 16             | 7.5        | 1.22                    | 45                                  | -32                            | 13    | 15     | 1400                             | T3        |
| -0137            | -0357   | -0577   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0138            | -0358   | -0578   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0139            | -0359   | -0579   | 20              | 160                    | 50                           | 8               | 32             | 8.5        | 0.71                    | 27                                  | -50                            | 25    | 25     | 1900                             | T4        |
| -0140            | -0360   | -0580   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0147            | -0367   | -0587   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0148            | -0368   | -0588   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0149            | -0369   | -0589   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0150            | -0370   | -0590   | 20              | 39                     | 60                           | 1               | 9              | 5          | 1.7                     | 90                                  | -28                            | 10.5  | 12     | 1110                             | T2        |
| -0151            | -0371   | -0591   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0152            | -0372   | -0592   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0153            | -0373   | -0593   | 20              | 50                     | 60                           | 2               | 12             | 5          | 1.33                    | 50                                  | -16                            | 10.5  | 12     | 1330                             | T3        |
| -0154            | -0374   | -0594   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0155            | -0375   | -0595   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0156            | -0376   | -0596   | 20              | 68                     | 60                           | 2               | 16             | 6.5        | 1.27                    | 50                                  | -32                            | 10.5  | 12     | 1365                             | T3        |
| -0157            | -0377   | -0597   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0158            | -0378   | -0598   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0159            | -0379   | -0599   | 20              | 140                    | 60                           | 8               | 32             | 8          | 0.76                    | 28                                  | -40                            | 20    | 20     | 1850                             | T4        |
| -0160            | -0380   | -0600   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0167            | -0387   | -0607   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0168            | -0388   | -0608   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0169            | -0389   | -0609   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0170            | -0390   | -0610   | 20              | 33                     | 75                           | 1               | 10             | 5          | 2.01                    | 90                                  | -24                            | 10.5  | 15     | 1000                             | T2        |
| -0171            | -0391   | -0611   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0172            | -0392   | -0612   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0173            | -0393   | -0613   | 20              | 40                     | 75                           | 2               | 12             | 4.5        | 1.5                     | 60                                  | -16                            | 10.5  | 12     | 1250                             | T3        |
| -0174            | -0394   | -0614   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0175            | -0395   | -0615   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0176            | -0396   | -0616   | 20              | 56                     | 75                           | 2               | 17             | 5.5        | 1.31                    | 60                                  | -28                            | 10.5  | 15     | 1335                             | T3        |
| -0177            | -0397   | -0617   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0178            | -0398   | -0618   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0179            | -0399   | -0619   | 20              | 110                    | 75                           | 9               | 36             | 6          | 0.73                    | 29                                  | -35                            | 20    | 20     | 1850                             | T4        |
| -0180            | -0400   | -0620   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0187            | -0407   | -0627   | 20              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0188            | -0408   | -0628   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0189            | -0409   | -0629   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0190            | -0410   | -0630   | 20              | 22                     | 100                          | 1               | 9              | 3.75       | 2.26                    | 100                                 | -16                            | 8     | 8      | 965                              | T2        |
| -0191            | -0411   | -0631   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0192            | -0412   | -0632   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0193            | -0413   | -0633   | 20              | 30                     | 100                          | 2               | 12             | 3.5        | 1.55                    | 80                                  | -16                            | 8     | 8      | 1240                             | T3        |
| -0194            | -0414   | -0634   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0195            | -0415   | -0635   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0196            | -0416   | -0636   | 20              | 43                     | 100                          | 2               | 17             | 4.25       | 1.31                    | 70                                  | -20                            | 8     | 8      | 1335                             | T3        |
| -0197            | -0417   | -0637   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0198            | -0418   | -0638   | 5               |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0199            | -0419   | -0639   | 20              | 86                     | 100                          | 9               | 36             | 5          | 0.77                    | 30                                  | -25                            | 15    | 15     | 1800                             | T4        |
| -0200            | -0420   | -0640   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.





# MIL-PRF-39006 Series



## Military Conventional Wet Tantalum


### M39006 /31 RATINGS AND DASH NUMBER REFERENCE

| M39006/31 Dashes |         |         | Tolerance ± (%) | Cap (µF) 25°C at 120Hz | DC Rated Voltage (V) at 85°C | DC Leakage (µA) |                | DF max (%) | ESR max (Ohms) at 120Hz | Impedance max (Ohms) -55°C at 120Hz | Maximum Capacitance Change (%) |       |        | AC Ripple (mA rms) 85°C at 40kHz | Case Size |
|------------------|---------|---------|-----------------|------------------------|------------------------------|-----------------|----------------|------------|-------------------------|-------------------------------------|--------------------------------|-------|--------|----------------------------------|-----------|
| M Level          | P Level | R Level |                 |                        |                              | +25°C           | +85°C & +125°C |            |                         |                                     | -55°C                          | +85°C | +125°C |                                  |           |
| -0003            | -0091   | -0179   | 20              | 820                    | 6                            | 3               | 14             | 77.5       | 1.26                    | 18                                  | -88                            | 16    | 20     | 1500                             | T2        |
| -0004            | -0092   | -0180   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0005            | -0093   | -0181   | 20              | 1500                   | 6                            | 5               | 20             | 86         | 0.76                    | 18                                  | -90                            | 20    | 25     | 1900                             | T3        |
| -0006            | -0094   | -0182   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0007            | -0095   | -0183   | 20              | 2200                   | 6                            | 6               | 24             | 85         | 0.52                    | 13                                  | -90                            | 25    | 30     | 2300                             | T4        |
| -0008            | -0096   | -0184   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0011            | -0099   | -0187   | 20              | 680                    | 8                            | 3               | 14             | 65         | 1.27                    | 22                                  | -83                            | 16    | 20     | 1500                             | T2        |
| -0012            | -0100   | -0188   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0013            | -0101   | -0189   | 20              | 1500                   | 8                            | 5               | 20             | 85         | 0.75                    | 18                                  | -90                            | 20    | 25     | 1900                             | T3        |
| -0014            | -0102   | -0190   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0015            | -0103   | -0191   | 20              | 1800                   | 8                            | 7               | 25             | 69         | 0.51                    | 14                                  | -90                            | 25    | 30     | 2300                             | T4        |
| -0016            | -0104   | -0192   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0019            | -0107   | -0195   | 20              | 560                    | 10                           | 3               | 16             | 53         | 1.26                    | 27                                  | -77                            | 16    | 20     | 1450                             | T2        |
| -0020            | -0108   | -0196   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0021            | -0109   | -0197   | 20              | 1200                   | 10                           | 5               | 20             | 68.5       | 0.76                    | 18                                  | -88                            | 20    | 25     | 1850                             | T3        |
| -0022            | -0110   | -0198   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0023            | -0111   | -0199   | 20              | 1500                   | 10                           | 7               | 25             | 57         | 0.51                    | 15                                  | -88                            | 25    | 30     | 2300                             | T4        |
| -0024            | -0112   | -0200   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0027            | -0115   | -0203   | 20              | 390                    | 15                           | 3               | 16             | 37         | 1.26                    | 31                                  | -66                            | 16    | 20     | 1450                             | T2        |
| -0028            | -0116   | -0204   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0029            | -0117   | -0205   | 20              | 820                    | 15                           | 6               | 24             | 55.5       | 0.9                     | 22                                  | -77                            | 20    | 25     | 1800                             | T3        |
| -0030            | -0118   | -0206   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0031            | -0119   | -0207   | 20              | 1000                   | 15                           | 8               | 32             | 46         | 0.61                    | 17                                  | -77                            | 25    | 30     | 2300                             | T4        |
| -0032            | -0120   | -0208   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0035            | -0123   | -0211   | 20              | 270                    | 25                           | 3               | 16             | 27.5       | 1.35                    | 33                                  | -62                            | 13    | 16     | 1400                             | T2        |
| -0036            | -0124   | -0212   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0037            | -0125   | -0213   | 20              | 560                    | 25                           | 7               | 28             | 38         | 0.9                     | 24                                  | -72                            | 20    | 25     | 1750                             | T3        |
| -0038            | -0126   | -0214   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0039            | -0127   | -0215   | 20              | 680                    | 25                           | 8               | 32             | 31.5       | 0.62                    | 19                                  | -72                            | 25    | 30     | 2100                             | T4        |
| -0040            | -0128   | -0216   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0043            | -0131   | -0219   | 20              | 220                    | 30                           | 3               | 16             | 21         | 1.27                    | 36                                  | -60                            | 13    | 16     | 1200                             | T2        |
| -0044            | -0132   | -0220   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0045            | -0133   | -0221   | 20              | 470                    | 30                           | 8               | 32             | 32         | 0.91                    | 25                                  | -65                            | 20    | 25     | 1500                             | T3        |
| -0046            | -0134   | -0222   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0047            | -0135   | -0223   | 20              | 560                    | 30                           | 9               | 36             | 27.5       | 0.65                    | 20                                  | -65                            | 25    | 30     | 2000                             | T4        |
| -0048            | -0136   | -0224   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0051            | -0139   | -0227   | 20              | 120                    | 50                           | 4               | 24             | 11.3       | 1.25                    | 49                                  | -42                            | 12    | 15     | 1200                             | T2        |
| -0052            | -0140   | -0228   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0053            | -0141   | -0229   | 20              | 270                    | 50                           | 8               | 32             | 18.5       | 0.91                    | 29                                  | -46                            | 20    | 25     | 1450                             | T3        |
| -0054            | -0142   | -0230   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0055            | -0143   | -0231   | 20              | 330                    | 50                           | 9               | 36             | 19         | 0.77                    | 22                                  | -46                            | 25    | 30     | 1900                             | T4        |
| -0056            | -0144   | -0232   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0059            | -0147   | -0235   | 20              | 100                    | 60                           | 4               | 20             | 9.5        | 1.26                    | 54                                  | -36                            | 12    | 15     | 1100                             | T2        |
| -0060            | -0148   | -0236   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0061            | -0149   | -0237   | 20              | 220                    | 60                           | 8               | 32             | 15         | 0.91                    | 29                                  | -40                            | 16    | 20     | 1400                             | T3        |
| -0062            | -0150   | -0238   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0063            | -0151   | -0239   | 20              | 270                    | 60                           | 9               | 36             | 13.5       | 0.67                    | 23                                  | -45                            | 20    | 25     | 1850                             | T4        |
| -0064            | -0152   | -0240   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0067            | -0155   | -0243   | 20              | 82                     | 75                           | 4               | 24             | 7.6        | 1.23                    | 63                                  | -30                            | 12    | 15     | 1000                             | T2        |
| -0068            | -0156   | -0244   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0069            | -0157   | -0245   | 20              | 180                    | 75                           | 9               | 36             | 12.2       | 0.9                     | 30                                  | -35                            | 16    | 20     | 1300                             | T3        |
| -0070            | -0158   | -0246   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0071            | -0159   | -0247   | 20              | 220                    | 75                           | 10              | 40             | 18.5       | 1.12                    | 24                                  | -40                            | 20    | 25     | 1800                             | T4        |
| -0072            | -0160   | -0248   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0075            | -0163   | -0251   | 20              | 39                     | 100                          | 5               | 24             | 5.2        | 1.77                    | 80                                  | -20                            | 12    | 15     | 1300                             | T2        |
| -0076            | -0164   | -0252   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0077            | -0165   | -0253   | 20              | 68                     | 100                          | 10              | 40             | 5.65       | 1.11                    | 40                                  | -30                            | 14    | 16     | 1600                             | T3        |
| -0078            | -0166   | -0254   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |
| -0079            | -0167   | -0255   | 20              | 120                    | 100                          | 12              | 48             | 12.5       | 1.38                    | 30                                  | -35                            | 15    | 17     | 2000                             | T4        |
| -0080            | -0168   | -0256   | 10              |                        |                              |                 |                |            |                         |                                     |                                |       |        |                                  |           |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.



## COTS-Plus Conventional Wet Tantalum




The TWC series represents a COTS-Plus version of conventional wet electrolytic tantalum capacitors. This data sheet incorporates all ratings available in MIL-PRF-39006 /22 /25 /30 and /31. Contact the factory about cap and voltage design possibilities beyond those contained in this datasheet.

This design includes a welded tantalum can and header assembly that provides a hermetic seal to withstand harsh environments and includes selected Group A testing from MIL-PRF-39006.

For military qualified versions please refer to the MIL-PRF-39006 datasheet located on the AVX website.

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)

| DSCC Case Size | AVX Case Size | L                              |  | D                           |  | E                     |               |
|----------------|---------------|--------------------------------|--|-----------------------------|--|-----------------------|---------------|
|                |               | +0.79 (0.031)<br>-0.41 (0.016) |  | Basic Case<br>±0.41 (0.016) |  | Insulated Case<br>Max | ±6.35 (0.250) |
| T1             | A             | 11.51 (0.453)                  |  | 4.78 (0.188)                |  | 5.56 (0.219)          | 38.10 (1.500) |
| T2             | B             | 16.28 (0.641)                  |  | 7.14 (0.281)                |  | 7.92 (0.312)          | 57.15 (2.250) |
| T3             | D             | 19.46 (0.766)                  |  | 9.52 (0.375)                |  | 10.31 (0.406)         | 57.15 (2.250) |
| T4             | E             | 26.97 (1.062)                  |  | 9.52 (0.375)                |  | 10.31 (0.406)         | 57.15 (2.250) |

### VOLTAGE RATINGS (Operating Temperature -55°C to 125°C)

| Voltage (DC)               |       |     |     |      |      |      |      |      |    |      |     |     |  |
|----------------------------|-------|-----|-----|------|------|------|------|------|----|------|-----|-----|--|
| Rated Voltage: ( $V_r$ )   | 85°C  | 6   | 8   | 10   | 15   | 25   | 30   | 50   | 60 | 75   | 100 | 125 |  |
| Derated Voltage: ( $V_d$ ) | 125°C | 4   | 5   | 6    | 10   | 15   | 20   | 30   | 40 | 50   | 65  | 85  |  |
| Surge Voltage: ( $V_s$ )   | 85°C  | 6.9 | 9.2 | 11.5 | 17.3 | 28.8 | 34.5 | 57.5 | 69 | 86.3 | 115 | 144 |  |


# TWC Series



## COTS-Plus Conventional Wet Tantalum

### HOW TO ORDER


#### AVX PART NUMBER:



\*High vibration qualified parts are currently under development. Please contact the factory for additional details and availability.



#### SPACE LEVEL OPTIONS TO SRW9000\*:



**Not RoHS Compliant**

\*Check with factory for availability and testing details.

### RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/</sup>

| Frequency of Applied Ripple Current | Ambient Still Air Temperature (°C) | 120Hz |      |      |      | 800Hz |      |      |      | 1kHz |      |      |      |
|-------------------------------------|------------------------------------|-------|------|------|------|-------|------|------|------|------|------|------|------|
|                                     |                                    | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |
| % of                                | 100%                               | 0.60  | 0.39 | -    | -    | 0.71  | 0.43 | -    | -    | 0.72 | 0.45 | -    | -    |
| 85°C                                | 90%                                | 0.60  | 0.46 | -    | -    | 0.71  | 0.55 | -    | -    | 0.72 | 0.55 | -    | -    |
| Rated                               | 80%                                | 0.60  | 0.52 | 0.35 | -    | 0.71  | 0.62 | 0.42 | -    | 0.72 | 0.62 | 0.42 | -    |
| Peak                                | 70%                                | 0.60  | 0.58 | 0.44 | -    | 0.71  | 0.69 | 0.52 | -    | 0.72 | 0.70 | 0.52 | -    |
| Voltage                             | 66-2/3%                            | 0.60  | 0.60 | 0.46 | 0.27 | 0.71  | 0.71 | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |

| Frequency of Applied Ripple Current | Ambient Still Air Temperature (°C) | 10kHz |      |      |      | 40kHz |      |      |      | 100kHz |      |      |      |
|-------------------------------------|------------------------------------|-------|------|------|------|-------|------|------|------|--------|------|------|------|
|                                     |                                    | ≤55   | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |
| % of                                | 100%                               | 0.88  | 0.55 | -    | -    | 1.00  | 0.63 | -    | -    | 1.10   | 0.69 | -    | -    |
| 85°C                                | 90%                                | 0.88  | 0.67 | -    | -    | 1.00  | 0.77 | -    | -    | 1.10   | 0.85 | -    | -    |
| Rated                               | 80%                                | 0.88  | 0.76 | 0.52 | -    | 1.00  | 0.87 | 0.59 | -    | 1.10   | 0.96 | 0.65 | -    |
| Peak                                | 70%                                | 0.88  | 0.85 | 0.64 | -    | 1.00  | 0.97 | 0.73 | -    | 1.10   | 1.07 | 0.80 | -    |
| Voltage                             | 66-2/3%                            | 0.88  | 0.88 | 0.68 | 0.40 | 1.00  | 1.00 | 0.77 | 0.45 | 1.10   | 1.10 | 0.85 | 0.50 |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.



### STANDARD RATINGS & PART NUMBER REFERENCE

| AVX Part Number     | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | DC Leakage (µA) |                   | DF<br>(Max) | ESR Max<br>(Ohms)<br>at 120Hz | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance<br>Change (%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |     |
|---------------------|------------------------------|------------------------------------|-----------------|-------------------|-------------|-------------------------------|---|-----------------------------------|-------|--------|--|-----------|-----|
|                     |                              |                                    | +25°C           | +85°C<br>& +125°C |             |                               |   | -55°C                             | +85°C | +125°C |  | Standard  | AVX |
| TWCA306*006□CSZ0*00 | 30                           | 6                                  | 1               | 2                 | 9           | 3.98                          | 100                                       | -40                               | 10.5  | 12     | 820                                    | T1        | A   |
| TWCA306*006□LSZ0*00 |                              |                                    |                 |                   | 4.5         | 1.99                          |   |                                   |       |        |  |           |     |
| TWCA686*006□CSZ0*00 | 68                           | 6                                  | 1               | 2                 | 15          | 3.16                          | 60  | -40                               | 14    | 16     | 960                                    | T1        | A   |
| TWCA686*006□LSZ0*00 |                              |                                    |                 |                   | 7.5         | 1.58                          |   |                                   |       |        |  |           |     |
| TWCB147*006□CSZ0*00 | 140                          | 6                                  | 1               | 3                 | 21          | 1.99                          | 40  | -40                               | 14    | 16     | 1,200                                  | T2        | B   |
| TWCB147*006□LSZ0*00 |                              |                                    |                 |                   | 10.5        | 0.99                          |   |                                   |       |        |  |           |     |
| TWCB277*006□CSZ0*00 | 270                          | 6                                  | 1               | 6.5               | 45          | 2.21                          | 25  | -44                               | 17.5  | 20     | 1,375                                  | T2        | B   |
| TWCB277*006□LSZ0*00 |                              |                                    |                 |                   | 22.5        | 1.11                          |   |                                   |       |        |  |           |     |
| TWCD337*006□CSZ0*00 | 330                          | 6                                  | 2               | 7.9               | 36          | 1.45                          | 20  | -44                               | 14    | 16     | 1,800                                  | T3        | D   |
| TWCD337*006□LSZ0*00 |                              |                                    |                 |                   | 18          | 0.73                          |   |                                   |       |        |  |           |     |
| TWCD567*006□CSZ0*00 | 560                          | 6                                  | 2               | 13                | 55          | 1.3                           | 25  | -64                               | 17.5  | 20     | 1,900                                  | T3        | D   |
| TWCD567*006□LSZ0*00 |                              |                                    |                 |                   | 27.5        | 0.65                          |   |                                   |       |        |  |           |     |
| TWCE128*006□CSZ0*00 | 1,200                        | 6                                  | 3               | 14                | 90          | 1                             | 20  | -80                               | 25    | 25     | 2,265                                  | T4        | E   |
| TWCE128*006□LSZ0*00 |                              |                                    |                 |                   | 45          | 0.5                           |   |                                   |       |        |  |           |     |
| TWCA256*008□CSZ0*00 | 25                           | 8                                  | 1               | 2                 | 7.5         | 3.98                          | 100                                       | -40                               | 10.5  | 12     | 820                                    | T1        | A   |
| TWCA256*008□LSZ0*00 |                              |                                    |                 |                   | 3.75        | 1.99                          |   |                                   |       |        |  |           |     |
| TWCA566*008□CSZ0*00 | 56                           | 8                                  | 1               | 2                 | 14          | 3.32                          | 59  | -40                               | 14    | 16     | 900                                    | T1        | A   |
| TWCA566*008□LSZ0*00 |                              |                                    |                 |                   | 7           | 1.66                          |   |                                   |       |        |  |           |     |
| TWCB127*008□CSZ0*00 | 120                          | 8                                  | 1               | 2                 | 20          | 2.21                          | 50  | -44                               | 17.5  | 20     | 1,220                                  | T2        | B   |
| TWCB127*008□LSZ0*00 |                              |                                    |                 |                   | 10          | 1.11                          |   |                                   |       |        |  |           |     |
| TWCB227*008□CSZ0*00 | 220                          | 8                                  | 1               | 7                 | 37          | 2.23                          | 30  | -44                               | 17.5  | 20     | 1,370                                  | T2        | B   |
| TWCB227*008□LSZ0*00 |                              |                                    |                 |                   | 18.5        | 1.12                          |   |                                   |       |        |  |           |     |
| TWCD297*008□CSZ0*00 | 290                          | 8                                  | 2               | 6                 | 34          | 1.56                          | 25  | -64                               | 17.5  | 20     | 1,770                                  | T3        | D   |
| TWCD297*008□LSZ0*00 |                              |                                    |                 |                   | 17          | 0.78                          |   |                                   |       |        |  |           |     |
| TWCD437*008□CSZ0*00 | 430                          | 8                                  | 2               | 14                | 46          | 1.42                          | 25  | -64                               | 17.5  | 20     | 1,825                                  | T3        | D   |
| TWCD437*008□LSZ0*00 |                              |                                    |                 |                   | 23          | 0.71                          |   |                                   |       |        |  |           |     |
| TWCE857*008□CSZ0*00 | 850                          | 8                                  | 4               | 16                | 60          | 0.94                          | 22  | -80                               | 25    | 25     | 2,330                                  | T4        | E   |
| TWCE857*008□LSZ0*00 |                              |                                    |                 |                   | 30          | 0.47                          |   |                                   |       |        |  |           |     |
| TWCA206*010□CSZ0*00 | 20                           | 10                                 | 1               | 2                 | 6           | 3.98                          | 175                                       | -32                               | 10.5  | 12     | 820                                    | T1        | A   |
| TWCA206*010□LSZ0*00 |                              |                                    |                 |                   | 3           | 1.99                          |   |                                   |       |        |  |           |     |
| TWCA476*010□CSZ0*00 | 47                           | 10                                 | 1               | 2                 | 13          | 3.67                          | 100                                       | -36                               | 14    | 16     | 855                                    | T1        | A   |
| TWCA476*010□LSZ0*00 |                              |                                    |                 |                   | 6.5         | 1.84                          |   |                                   |       |        |  |           |     |
| TWCB107*010□CSZ0*00 | 100                          | 10                                 | 1               | 4                 | 15          | 1.99                          | 60  | -36                               | 14    | 16     | 1,200                                  | T2        | B   |
| TWCB107*010□LSZ0*00 |                              |                                    |                 |                   | 7.5         | 0.99                          |   |                                   |       |        |  |           |     |
| TWCB187*010□CSZ0*00 | 180                          | 10                                 | 1               | 7                 | 30          | 2.21                          | 40  | -36                               | 14    | 16     | 1,365                                  | T2        | B   |
| TWCB187*010□LSZ0*00 |                              |                                    |                 |                   | 15          | 1.11                          |   |                                   |       |        |  |           |     |
| TWCD257*010□CSZ0*00 | 250                          | 10                                 | 2               | 10                | 30          | 1.59                          | 30  | -40                               | 14    | 16     | 1,720                                  | T3        | D   |
| TWCD257*010□LSZ0*00 |                              |                                    |                 |                   | 15          | 0.8                           |   |                                   |       |        |  |           |     |
| TWCD397*010□CSZ0*00 | 390                          | 10                                 | 2               | 16                | 44          | 1.5                           | 25  | -64                               | 17.5  | 20     | 1,800                                  | T3        | D   |
| TWCD397*010□LSZ0*00 |                              |                                    |                 |                   | 22          | 0.75                          |   |                                   |       |        |  |           |     |
| TWCE757*010□CSZ0*00 | 750                          | 10                                 | 4               | 16                | 50          | 0.88                          | 23  | -80                               | 25    | 25     | 2,360                                  | T4        | E   |
| TWCE757*010□LSZ0*00 |                              |                                    |                 |                   | 25          | 0.44                          |   |                                   |       |        |  |           |     |
| TWCA156*015□CSZ0*00 | 15                           | 15                                 | 1               | 2                 | 5           | 4.42                          | 155                                       | -24                               | 10.5  | 12     | 780                                    | T1        | A   |
| TWCA156*015□LSZ0*00 |                              |                                    |                 |                   | 2.5         | 2.21                          |   |                                   |       |        |  |           |     |
| TWCA336*015□CSZ0*00 | 33                           | 15                                 | 1               | 2                 | 10          | 4.02                          | 90  | -28                               | 14    | 16     | 820                                    | T1        | A   |
| TWCA336*015□LSZ0*00 |                              |                                    |                 |                   | 5           | 2.01                          |   |                                   |       |        |  |           |     |
| TWCB706*015□CSZ0*00 | 70                           | 15                                 | 1               | 4                 | 13          | 2.46                          | 75  | -28                               | 14    | 16     | 1,150                                  | T2        | B   |
| TWCB706*015□LSZ0*00 |                              |                                    |                 |                   | 6.5         | 1.23                          |   |                                   |       |        |  |           |     |
| TWCB127*015□CSZ0*00 | 120                          | 15                                 | 1               | 7                 | 18          | 1.99                          | 50  | -28                               | 17.5  | 20     | 1,450                                  | T2        | B   |
| TWCB127*015□LSZ0*00 |                              |                                    |                 |                   | 9           | 0.99                          |   |                                   |       |        |  |           |     |
| TWCD177*015□CSZ0*00 | 170                          | 15                                 | 2               | 10                | 25          | 1.95                          | 35  | -32                               | 14    | 16     | 1,480                                  | T3        | D   |
| TWCD177*015□LSZ0*00 |                              |                                    |                 |                   | 12.5        | 0.98                          |   |                                   |       |        |  |           |     |
| TWCD277*015□CSZ0*00 | 270                          | 15                                 | 2               | 16                | 32          | 1.57                          | 30  | -56                               | 17.5  | 20     | 1,740                                  | T3        | D   |
| TWCD277*015□LSZ0*00 |                              |                                    |                 |                   | 16          | 0.79                          |   |                                   |       |        |  |           |     |
| TWCE547*015□CSZ0*00 | 540                          | 15                                 | 6               | 24                | 40          | 0.98                          | 23  | -80                               | 25    | 25     | 2,330                                  | T4        | E   |
| TWCE547*015□LSZ0*00 |                              |                                    |                 |                   | 20          | 0.49                          |   |                                   |       |        |  |           |     |
| TWCA106*025□CSZ0*00 | 10                           | 25                                 | 1               | 2                 | 4           | 5.31                          | 220                                       | -16                               | 8     | 9      | 715                                    | T1        | A   |
| TWCA106*025□LSZ0*00 |                              |                                    |                 |                   | 2           | 2.66                          |   |                                   |       |        |  |           |     |
| TWCA226*025□CSZ0*00 | 22                           | 25                                 | 1               | 2                 | 6.6         | 3.98                          | 140                                       | -20                               | 10.5  | 12     | 825                                    | T1        | A   |
| TWCA226*025□LSZ0*00 |                              |                                    |                 |                   | 3.3         | 1.99                          |   |                                   |       |        |  |           |     |
| TWCB506*025□CSZ0*00 | 50                           | 25                                 | 1               | 2                 | 11          | 2.92                          | 70  | -28                               | 13    | 15     | 1,130                                  | T2        | B   |
| TWCB506*025□LSZ0*00 |                              |                                    |                 |                   | 5.5         | 1.46                          |   |                                   |       |        |  |           |     |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

## COTS-Plus Conventional Wet Tantalum

### STANDARD RATINGS & PART NUMBER REFERENCE

| AVX Part Number     | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | DC Leakage (µA) |                   | DF<br>(Max) | ESR Max<br>(Ohms)<br>at 120Hz | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance<br>Change (%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |     |
|---------------------|------------------------------|------------------------------------|-----------------|-------------------|-------------|-------------------------------|---|-----------------------------------|-------|--------|--|-----------|-----|
|                     |                              |                                    | +25°C           | +85°C<br>& +125°C |             |                               |   | -55°C                             | +85°C | +125°C |  | Standard  | AVX |
| TWCB107*025□CSZ0^00 | 100                          | 25                                 | 1               | 10                | 15          | 1.99                          | 50  | -28                               | 13    | 15     | 1,435                                  | T2        | B   |
| TWCB107*025□LSZ0^00 |                              |                                    |                 |                   | 7.5         | 0.99                          |   |                                   |       |        |  |           |     |
| TWCD127*025□CSZ0^00 | 120                          | 25                                 | 2               | 6                 | 21          | 2.32                          | 38  | -32                               | 13    | 15     | 1,450                                  | T3        | D   |
| TWCD127*025□LSZ0^00 |                              |                                    |                 |                   | 10.5        | 1.16                          |   |                                   |       |        |  |           |     |
| TWCD187*025□CSZ0^00 | 180                          | 25                                 | 2               | 18                | 26          | 1.92                          | 32  | -48                               | 13    | 15     | 1,525                                  | T3        | D   |
| TWCD187*025□LSZ0^00 |                              |                                    |                 |                   | 13          | 0.96                          |   |                                   |       |        |  |           |     |
| TWCE357*025□CSZ0^00 | 350                          | 25                                 | 7               | 28                | 35          | 1.33                          | 24  | -70                               | 25    | 25     | 1,970                                  | T4        | E   |
| TWCE357*025□LSZ0^00 |                              |                                    |                 |                   | 17.5        | 0.67                          |   |                                   |       |        |  |           |     |
| TWCA805*030□CSZ0^00 | 8                            | 30                                 | 1               | 2                 | 4           | 6.64                          | 275                                       | -16                               | 8     | 12     | 640                                    | T1        | A   |
| TWCA805*030□LSZ0^00 |                              |                                    |                 |                   | 2           | 3.32                          |   |                                   |       |        |  |           |     |
| TWCA156*030□CSZ0^00 | 15                           | 30                                 | 1               | 2                 | 5           | 4.42                          | 175                                       | -20                               | 10.5  | 12     | 780                                    | T1        | A   |
| TWCA156*030□LSZ0^00 |                              |                                    |                 |                   | 2.5         | 2.21                          |   |                                   |       |        |  |           |     |
| TWCB406*030□CSZ0^00 | 40                           | 30                                 | 1               | 5                 | 10          | 3.32                          | 65  | -24                               | 10.5  | 12     | 1,120                                  | T2        | B   |
| TWCB406*030□LSZ0^00 |                              |                                    |                 |                   | 5           | 1.66                          |   |                                   |       |        |  |           |     |
| TWCB686*030□CSZ0^00 | 68                           | 30                                 | 1               | 8                 | 13          | 2.54                          | 60  | -24                               | 13    | 15     | 1,285                                  | T2        | B   |
| TWCB686*030□LSZ0^00 |                              |                                    |                 |                   | 6.5         | 1.27                          |   |                                   |       |        |  |           |     |
| TWCD107*030□CSZ0^00 | 100                          | 30                                 | 2               | 12                | 17          | 2.26                          | 40  | -28                               | 10.5  | 12     | 1,450                                  | T3        | D   |
| TWCD107*030□LSZ0^00 |                              |                                    |                 |                   | 8.5         | 1.13                          |   |                                   |       |        |  |           |     |
| TWCD157*030□CSZ0^00 | 150                          | 30                                 | 2               | 18                | 23          | 2.03                          | 35  | -48                               | 13    | 15     | 1,525                                  | T3        | D   |
| TWCD157*030□LSZ0^00 |                              |                                    |                 |                   | 11.5        | 1.02                          |   |                                   |       |        |  |           |     |
| TWCE307*030□CSZ0^00 | 300                          | 30                                 | 8               | 32                | 31          | 1.37                          | 25  | -60                               | 25    | 25     | 1,950                                  | T4        | E   |
| TWCE307*030□LSZ0^00 |                              |                                    |                 |                   | 15.5        | 0.69                          |   |                                   |       |        |  |           |     |
| TWCA505*050□CSZ0^00 | 5                            | 50                                 | 1               | 2                 | 3           | 7.96                          | 400                                       | -16                               | 5     | 6      | 580                                    | T1        | A   |
| TWCA505*050□LSZ0^00 |                              |                                    |                 |                   | 1.5         | 3.98                          |   |                                   |       |        |  |           |     |
| TWCA106*050□CSZ0^00 | 10                           | 50                                 | 1               | 2                 | 4           | 5.31                          | 250                                       | -24                               | 8     | 9      | 715                                    | T1        | A   |
| TWCA106*050□LSZ0^00 |                              |                                    |                 |                   | 2           | 2.66                          |   |                                   |       |        |  |           |     |
| TWCB256*050□CSZ0^00 | 25                           | 50                                 | 1               | 5                 | 8           | 4.25                          | 95  | -20                               | 10.5  | 12     | 1,005                                  | T2        | B   |
| TWCB256*050□LSZ0^00 |                              |                                    |                 |                   | 4           | 2.13                          |   |                                   |       |        |  |           |     |
| TWCB476*050□CSZ0^00 | 47                           | 50                                 | 1               | 9                 | 11          | 3.11                          | 70  | -28                               | 13    | 15     | 1,155                                  | T2        | B   |
| TWCB476*050□LSZ0^00 |                              |                                    |                 |                   | 5.5         | 1.56                          |   |                                   |       |        |  |           |     |
| TWCD606*050□CSZ0^00 | 60                           | 50                                 | 2               | 12                | 12          | 2.65                          | 45  | -16                               | 10.5  | 12     | 1,335                                  | T3        | D   |
| TWCD606*050□LSZ0^00 |                              |                                    |                 |                   | 6           | 1.33                          |   |                                   |       |        |  |           |     |
| TWCD826*050□CSZ0^00 | 82                           | 50                                 | 2               | 16                | 15          | 2.43                          | 45  | -32                               | 13    | 15     | 1,400                                  | T3        | D   |
| TWCD826*050□LSZ0^00 |                              |                                    |                 |                   | 7.5         | 1.22                          |   |                                   |       |        |  |           |     |
| TWCE167*050□CSZ0^00 | 160                          | 50                                 | 8               | 32                | 17          | 1.41                          | 27  | -50                               | 25    | 25     | 1,900                                  | T4        | E   |
| TWCE167*050□LSZ0^00 |                              |                                    |                 |                   | 8.5         | 0.71                          |   |                                   |       |        |  |           |     |
| TWCA405*060□CSZ0^00 | 4                            | 60                                 | 1               | 2                 | 2.8         | 9.29                          | 550                                       | -16                               | 5     | 6      | 525                                    | T1        | A   |
| TWCA405*060□LSZ0^00 |                              |                                    |                 |                   | 1.4         | 4.65                          |   |                                   |       |        |  |           |     |
| TWCA825*060□CSZ0^00 | 8.2                          | 60                                 | 1               | 2                 | 4           | 6.47                          | 275                                       | -24                               | 8     | 9      | 625                                    | T1        | A   |
| TWCA825*060□LSZ0^00 |                              |                                    |                 |                   | 2           | 3.24                          |   |                                   |       |        |  |           |     |
| TWCB206*060□CSZ0^00 | 20                           | 60                                 | 1               | 5                 | 7           | 4.64                          | 105                                       | -16                               | 10.5  | 12     | 930                                    | T2        | B   |
| TWCB206*060□LSZ0^00 |                              |                                    |                 |                   | 3.5         | 2.32                          |   |                                   |       |        |  |           |     |
| TWCB396*060□CSZ0^00 | 39                           | 60                                 | 1               | 9                 | 10          | 3.4                           | 90  | -28                               | 10.5  | 12     | 1,110                                  | T2        | B   |
| TWCB396*060□LSZ0^00 |                              |                                    |                 |                   | 5           | 1.7                           |   |                                   |       |        |  |           |     |
| TWCD506*060□CSZ0^00 | 50                           | 60                                 | 2               | 12                | 10          | 2.65                          | 50  | -16                               | 10.5  | 12     | 1,330                                  | T3        | D   |
| TWCD506*060□LSZ0^00 |                              |                                    |                 |                   | 5           | 1.33                          |   |                                   |       |        |  |           |     |
| TWCB686*060□CSZ0^00 | 68                           | 60                                 | 2               | 16                | 13          | 2.54                          | 50  | -32                               | 10.5  | 12     | 1,365                                  | T3        | D   |
| TWCD686*060□LSZ0^00 |                              |                                    |                 |                   | 7           | 1.27                          |   |                                   |       |        |  |           |     |
| TWCE147*060□CSZ0^00 | 140                          | 60                                 | 8               | 32                | 16          | 1.52                          | 28  | -40                               | 20    | 20     | 1,850                                  | T4        | E   |
| TWCE147*060□LSZ0^00 |                              |                                    |                 |                   | 8           | 0.76                          |   |                                   |       |        |  |           |     |
| TWCA355*075□CSZ0^00 | 3.5                          | 75                                 | 1               | 2                 | 2.5         | 9.48                          | 650                                       | -16                               | 5     | 6      | 525                                    | T1        | A   |
| TWCA355*075□LSZ0^00 |                              |                                    |                 |                   | 1.25        | 4.74                          |   |                                   |       |        |  |           |     |
| TWCA685*075□CSZ0^00 | 6.8                          | 75                                 | 1               | 2                 | 3.5         | 6.83                          | 300                                       | -20                               | 8     | 9      | 610                                    | T1        | A   |
| TWCA685*075□LSZ0^00 |                              |                                    |                 |                   | 1.75        | 3.42                          |   |                                   |       |        |  |           |     |
| TWCB156*075□CSZ0^00 | 15                           | 75                                 | 1               | 5                 | 6           | 5.31                          | 150                                       | -16                               | 8     | 9      | 890                                    | T2        | B   |
| TWCB156*075□LSZ0^00 |                              |                                    |                 |                   | 3           | 2.66                          |   |                                   |       |        |  |           |     |
| TWCB336*075□CSZ0^00 | 33                           | 75                                 | 1               | 10                | 10          | 4.02                          | 90  | -24                               | 10.5  | 15     | 1,000                                  | T2        | B   |
| TWCB336*075□LSZ0^00 |                              |                                    |                 |                   | 5           | 2.01                          |   |                                   |       |        |  |           |     |
| TWCD406*075□CSZ0^00 | 40                           | 75                                 | 2               | 12                | 9           | 2.99                          | 60  | -16                               | 10.5  | 12     | 1,250                                  | T3        | D   |
| TWCD406*075□LSZ0^00 |                              |                                    |                 |                   | 4.5         | 1.5                           |   |                                   |       |        |  |           |     |
| TWCD566*075□CSZ0^00 | 56                           | 75                                 | 2               | 17                | 11          | 2.61                          | 60  | -28                               | 10.5  | 15     | 1,335                                  | T3        | D   |
| TWCD566*075□LSZ0^00 |                              |                                    |                 |                   | 5.5         | 1.31                          |   |                                   |       |        |  |           |     |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

### STANDARD RATINGS & PART NUMBER REFERENCE

| AVX Part Number     | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | DC Leakage (µA) |                   | DF<br>(Max) | ESR Max<br>(Ohms)<br>at 120Hz | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance<br>Change (%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |     |
|---------------------|------------------------------|------------------------------------|-----------------|-------------------|-------------|-------------------------------|---|-----------------------------------|-------|--------|--|-----------|-----|
|                     |                              |                                    | +25°C           | +85°C<br>& +125°C |             |                               |   | -55°C                             | +85°C | +125°C |  | Standard  | AVX |
| TWCE117*075□CSZ0^00 | 110                          | 75                                 | 9               | 36                | 12          | 1.45                          | 29  | -35                               | 20    | 20     | 1,850                                  | T4        | E   |
| TWCE117*075□LSZ0^00 |                              |                                    |                 |                   | 6           | 0.73                          |   |                                   |       |        |  |           |     |
| TWCA255*100□CSZ0^00 | 2.5                          | 100                                | 1               | 2                 | 2           | 10.62                         | 950                                       | -16                               | 7     | 8      | 505                                    | T1        | A   |
| TWCA255*100□LSZ0^00 |                              |                                    |                 |                   | 1           | 5.31                          |   |                                   |       |        |  |           |     |
| TWCA475*100□CSZ0^00 | 4.7                          | 100                                | 1               | 2                 | 3           | 8.47                          | 500                                       | -16                               | 7     | 8      | 565                                    | T1        | A   |
| TWCA475*100□LSZ0^00 |                              |                                    |                 |                   | 1.5         | 4.24                          |   |                                   |       |        |  |           |     |
| TWCB116*100□CSZ0^00 | 11                           | 100                                | 1               | 4                 | 5           | 6.03                          | 200                                       | -16                               | 8     | 8      | 835                                    | T2        | B   |
| TWCB116*100□LSZ0^00 |                              |                                    |                 |                   | 2.5         | 3.02                          |   |                                   |       |        |  |           |     |
| TWCB226*100□CSZ0^00 | 22                           | 100                                | 1               | 9                 | 7.5         | 4.52                          | 100                                       | -16                               | 8     | 8      | 965                                    | T2        | B   |
| TWCB226*100□LSZ0^00 |                              |                                    |                 |                   | 3.75        | 2.26                          |   |                                   |       |        |  |           |     |
| TWCD306*100□CSZ0^00 | 30                           | 100                                | 2               | 12                | 7           | 3.1                           | 80  | -16                               | 8     | 8      | 1,240                                  | T3        | D   |
| TWCD306*100□LSZ0^00 |                              |                                    |                 |                   | 3.5         | 1.56                          |   |                                   |       |        |  |           |     |
| TWCD436*100□CSZ0^00 | 43                           | 100                                | 2               | 17                | 8.5         | 2.62                          | 70  | -20                               | 8     | 8      | 1,335                                  | T3        | D   |
| TWCD436*100□LSZ0^00 |                              |                                    |                 |                   | 4.25        | 1.31                          |   |                                   |       |        |  |           |     |
| TWCE866*100□CSZ0^00 | 86                           | 100                                | 9               | 36                | 10          | 1.54                          | 30  | -25                               | 15    | 15     | 1,800                                  | T4        | E   |
| TWCE866*100□LSZ0^00 |                              |                                    |                 |                   | 5           | 0.77                          |   |                                   |       |        |  |           |     |
| TWCB905*125□CSZ0^00 | 9                            | 125                                | 1               | 5                 | 5           | 7.37                          | 240                                       | -16                               | 7     | 8      | 755                                    | T2        | B   |
| TWCB905*125□LSZ0^00 |                              |                                    |                 |                   | 2.5         | 3.69                          |   |                                   |       |        |  |           |     |
| TWCB146*125□CSZ0^00 | 14                           | 125                                | 1               | 7                 | 6           | 5.69                          | 167                                       | -16                               | 7     | 8      | 860                                    | T2        | B   |
| TWCB146*125□LSZ0^00 |                              |                                    |                 |                   | 3           | 2.85                          |   |                                   |       |        |  |           |     |
| TWCD186*125□CSZ0^00 | 18                           | 125                                | 2               | 9                 | 5           | 3.69                          | 129                                       | -16                               | 7     | 8      | 1,130                                  | T3        | D   |
| TWCD186*125□LSZ0^00 |                              |                                    |                 |                   | 2.5         | 1.85                          |   |                                   |       |        |  |           |     |
| TWCD256*125□CSZ0^00 | 25                           | 125                                | 2               | 13                | 6           | 3.18                          | 93  | -16                               | 7     | 8      | 1,200                                  | T3        | D   |
| TWCD256*125□LSZ0^00 |                              |                                    |                 |                   | 3           | 1.59                          |   |                                   |       |        |  |           |     |
| TWCE566*125□CSZ0^00 | 56                           | 125                                | 10              | 40                | 6.5         | 1.54                          | 32  | -25                               | 15    | 15     | 1,800                                  | T4        | E   |
| TWCE566*125□LSZ0^00 |                              |                                    |                 |                   | 3.25        | 0.77                          |   |                                   |       |        |  |           |     |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

### EXTENDED RATINGS & PART NUMBER REFERENCE

| AVX Part Number     | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | DC Leakage (µA) |                   | DF<br>(Max) | ESR Max<br>(Ohms)<br>at 120Hz | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance<br>Change (%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |     |
|---------------------|------------------------------|------------------------------------|-----------------|-------------------|-------------|-------------------------------|---|-----------------------------------|-------|--------|--|-----------|-----|
|                     |                              |                                    | +25°C           | +85°C<br>& +125°C |             |                               |   | -55°C                             | +85°C | +125°C |  | Standard  | AVX |
| TWCA227*006□CSZ0*00 | 220                          | 6                                  | 2               | 9                 | 50          | 3.02                          | 36  | -64                               | 13    | 16     | 1,000                                  | T1        | A   |
| TWCA227*006□LSZ0*00 |                              |                                    |                 |                   | 25          | 1.51                          |   |                                   |       |        |  |           |     |
| TWCB827*006□CSZ0*00 | 820                          | 6                                  | 3               | 14                | 155         | 2.51                          | 18  | -88                               | 16    | 20     | 1,500                                  | T2        | B   |
| TWCB827*006□LSZ0*00 |                              |                                    |                 |                   | 77.5        | 1.26                          |   |                                   |       |        |  |           |     |
| TWCD158*006□CSZ0*00 | 1,500                        | 6                                  | 5               | 20                | 172         | 1.52                          | 18  | -90                               | 20    | 25     | 1,900                                  | T3        | D   |
| TWCD158*006□LSZ0*00 |                              |                                    |                 |                   | 86          | 0.76                          |   |                                   |       |        |  |           |     |
| TWCE228*006□CSZ0*00 | 2,200                        | 6                                  | 6               | 24                | 170         | 1.03                          | 13  | -90                               | 25    | 30     | 2,300                                  | T4        | E   |
| TWCE228*006□LSZ0*00 |                              |                                    |                 |                   | 85          | 0.52                          |   |                                   |       |        |  |           |     |
| TWCA187*008□CSZ0*00 | 180                          | 8                                  | 2               | 9                 | 41          | 3.02                          | 45  | -60                               | 13    | 16     | 1,000                                  | T1        | A   |
| TWCA187*008□LSZ0*00 |                              |                                    |                 |                   | 20.5        | 1.51                          |   |                                   |       |        |  |           |     |
| TWCB687*008□CSZ0*00 | 680                          | 8                                  | 3               | 14                | 130         | 2.54                          | 22  | -83                               | 16    | 20     | 1,500                                  | T2        | B   |
| TWCB687*008□LSZ0*00 |                              |                                    |                 |                   | 65          | 1.27                          |   |                                   |       |        |  |           |     |
| TWCD158*008□CSZ0*00 | 1,500                        | 8                                  | 5               | 20                | 170         | 1.5                           | 18  | -90                               | 20    | 25     | 1,900                                  | T3        | D   |
| TWCD158*008□LSZ0*00 |                              |                                    |                 |                   | 85          | 0.75                          |   |                                   |       |        |  |           |     |
| TWCE188*008□CSZ0*00 | 1,800                        | 8                                  | 7               | 25                | 138         | 1.02                          | 14  | -90                               | 25    | 30     | 2,300                                  | T4        | E   |
| TWCE188*008□LSZ0*00 |                              |                                    |                 |                   | 69          | 0.51                          |   |                                   |       |        |  |           |     |
| TWCA157*010□CSZ0*00 | 150                          | 10                                 | 2               | 9                 | 34          | 3.01                          | 54  | -55                               | 13    | 16     | 900                                    | T1        | A   |
| TWCA157*010□LSZ0*00 |                              |                                    |                 |                   | 17          | 1.51                          |   |                                   |       |        |  |           |     |
| TWCB567*010□CSZ0*00 | 560                          | 10                                 | 3               | 16                | 106         | 2.51                          | 27  | -77                               | 16    | 20     | 1,450                                  | T2        | B   |
| TWCB567*010□LSZ0*00 |                              |                                    |                 |                   | 53          | 1.26                          |   |                                   |       |        |  |           |     |
| TWCD128*010□CSZ0*00 | 1,200                        | 10                                 | 5               | 20                | 137         | 1.51                          | 18  | -88                               | 20    | 25     | 1,850                                  | T3        | D   |
| TWCD128*010□LSZ0*00 |                              |                                    |                 |                   | 68.5        | 0.76                          |   |                                   |       |        |  |           |     |
| TWCE158*010□CSZ0*00 | 1,500                        | 10                                 | 7               | 25                | 114         | 1.01                          | 15  | -88                               | 25    | 30     | 2,300                                  | T4        | E   |
| TWCE158*010□LSZ0*00 |                              |                                    |                 |                   | 57          | 0.51                          |   |                                   |       |        |  |           |     |
| TWCA107*015□CSZ0*00 | 100                          | 15                                 | 2               | 9                 | 30          | 3.98                          | 72  | -44                               | 13    | 16     | 900                                    | T1        | A   |
| TWCA107*015□LSZ0*00 |                              |                                    |                 |                   | 15          | 1.99                          |   |                                   |       |        |  |           |     |
| TWCB397*015□CSZ0*00 | 390                          | 15                                 | 3               | 16                | 74          | 2.52                          | 31  | -66                               | 16    | 20     | 1,450                                  | T2        | B   |
| TWCB397*015□LSZ0*00 |                              |                                    |                 |                   | 37          | 1.26                          |   |                                   |       |        |  |           |     |
| TWCD827*015□CSZ0*00 | 820                          | 15                                 | 6               | 24                | 111         | 1.8                           | 22  | -77                               | 20    | 25     | 1,800                                  | T3        | D   |
| TWCD827*015□LSZ0*00 |                              |                                    |                 |                   | 55.5        | 0.9                           |   |                                   |       |        |  |           |     |
| TWCE108*015□CSZ0*00 | 1,000                        | 15                                 | 8               | 32                | 92          | 1.22                          | 17  | -77                               | 25    | 30     | 2,300                                  | T4        | E   |
| TWCE108*015□LSZ0*00 |                              |                                    |                 |                   | 46          | 0.61                          |   |                                   |       |        |  |           |     |
| TWCA686*025□CSZ0*00 | 68                           | 25                                 | 2               | 9                 | 22          | 4.29                          | 90  | -40                               | 12    | 15     | 850                                    | T1        | A   |
| TWCA686*025□LSZ0*00 |                              |                                    |                 |                   | 11          | 2.15                          |   |                                   |       |        |  |           |     |
| TWCB277*025□CSZ0*00 | 270                          | 25                                 | 3               | 16                | 55          | 2.7                           | 33  | -62                               | 13    | 16     | 1,400                                  | T2        | B   |
| TWCB277*025□LSZ0*00 |                              |                                    |                 |                   | 27.5        | 1.35                          |   |                                   |       |        |  |           |     |
| TWCD567*025□CSZ0*00 | 560                          | 25                                 | 7               | 28                | 76          | 1.8                           | 24  | -72                               | 20    | 25     | 1,750                                  | T3        | D   |
| TWCD567*025□LSZ0*00 |                              |                                    |                 |                   | 38          | 0.9                           |   |                                   |       |        |  |           |     |
| TWCE687*025□CSZ0*00 | 680                          | 25                                 | 8               | 32                | 63          | 1.23                          | 19  | -72                               | 25    | 30     | 2,100                                  | T4        | E   |
| TWCE687*025□LSZ0*00 |                              |                                    |                 |                   | 31.5        | 0.62                          |   |                                   |       |        |  |           |     |
| TWCA566*030□CSZ0*00 | 56                           | 30                                 | 2               | 9                 | 22          | 5.21                          | 100                                       | -38                               | 12    | 15     | 800                                    | T1        | A   |
| TWCA566*030□LSZ0*00 |                              |                                    |                 |                   | 11          | 2.61                          |   |                                   |       |        |  |           |     |
| TWCB227*030□CSZ0*00 | 220                          | 30                                 | 3               | 16                | 42          | 2.53                          | 36  | -60                               | 13    | 16     | 1,200                                  | T2        | B   |
| TWCB227*030□LSZ0*00 |                              |                                    |                 |                   | 21          | 1.27                          |   |                                   |       |        |  |           |     |
| TWCD477*030□CSZ0*00 | 470                          | 30                                 | 8               | 32                | 64          | 1.81                          | 25  | -65                               | 20    | 25     | 1,500                                  | T3        | D   |
| TWCD477*030□LSZ0*00 |                              |                                    |                 |                   | 32          | 0.91                          |   |                                   |       |        |  |           |     |
| TWCE567*030□CSZ0*00 | 560                          | 30                                 | 9               | 36                | 55          | 1.3                           | 20  | -65                               | 25    | 30     | 2,000                                  | T4        | E   |
| TWCE567*030□LSZ0*00 |                              |                                    |                 |                   | 27.5        | 0.65                          |   |                                   |       |        |  |           |     |
| TWCA336*050□CSZ0*00 | 33                           | 50                                 | 2               | 9                 | 12.3        | 4.95                          | 135                                       | -29                               | 10    | 12     | 700                                    | T1        | A   |
| TWCA336*050□LSZ0*00 |                              |                                    |                 |                   | 6.15        | 2.48                          |   |                                   |       |        |  |           |     |
| TWCB127*050□CSZ0*00 | 120                          | 50                                 | 4               | 24                | 22.5        | 2.49                          | 49  | -42                               | 12    | 15     | 1,200                                  | T2        | B   |
| TWCB127*050□LSZ0*00 |                              |                                    |                 |                   | 11.3        | 1.25                          |   |                                   |       |        |  |           |     |
| TWCD277*050□CSZ0*00 | 270                          | 50                                 | 8               | 32                | 37          | 1.82                          | 29  | -46                               | 20    | 25     | 1,450                                  | T3        | D   |
| TWCD277*050□LSZ0*00 |                              |                                    |                 |                   | 18.5        | 0.91                          |   |                                   |       |        |  |           |     |
| TWCE337*050□CSZ0*00 | 330                          | 50                                 | 9               | 36                | 38          | 1.53                          | 22  | -46                               | 25    | 30     | 1,900                                  | T4        | E   |
| TWCE337*050□LSZ0*00 |                              |                                    |                 |                   | 19          | 0.77                          |   |                                   |       |        |  |           |     |
| TWCA276*060□CSZ0*00 | 27                           | 60                                 | 3               | 12                | 10.2        | 5.01                          | 144                                       | -24                               | 10    | 12     | 700                                    | T1        | A   |
| TWCA276*060□LSZ0*00 |                              |                                    |                 |                   | 5.1         | 2.51                          |   |                                   |       |        |  |           |     |
| TWCB107*060□CSZ0*00 | 100                          | 60                                 | 4               | 20                | 19          | 2.52                          | 54  | -36                               | 12    | 15     | 1,100                                  | T2        | B   |
| TWCB107*060□LSZ0*00 |                              |                                    |                 |                   | 9.5         | 1.26                          |   |                                   |       |        |  |           |     |
| TWCD227*060□CSZ0*00 | 220                          | 60                                 | 8               | 32                | 30          | 1.81                          | 29  | -40                               | 16    | 20     | 1,400                                  | T3        | D   |
| TWCD227*060□LSZ0*00 |                              |                                    |                 |                   | 15          | 0.91                          |   |                                   |       |        |  |           |     |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

### EXTENDED RATINGS & PART NUMBER REFERENCE

| AVX Part Number     | Cap (µF)<br>25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at 85°C | DC Leakage (µA) |                   | DF<br>(Max) | ESR Max<br>(Ohms)<br>at 120Hz | Impedance<br>max (Ohms)<br>-55°C at 120Hz | Maximum Capacitance<br>Change (%) |       |        | AC Ripple<br>(mA rms)<br>85°C at 40kHz | Case Size |     |
|---------------------|------------------------------|------------------------------------|-----------------|-------------------|-------------|-------------------------------|---|-----------------------------------|-------|--------|--|-----------|-----|
|                     |                              |                                    | +25°C           | +85°C<br>& +125°C |             |                               |   | -55°C                             | +85°C | +125°C |  | Standard  | AVX |
| TWCE277*060□CSZ0^00 | 270                          | 60                                 | 9               | 36                | 27          | 1.33                          | 23  | -45                               | 20    | 25     | 1,850                                  | T4        | E   |
| TWCE277*060□LSZ0^00 |                              |                                    |                 |                   | 13.5        | 0.67                          |   |                                   |       |        |  |           |     |
| TWCA226*075□CSZ0^00 | 22                           | 75                                 | 3               | 12                | 8.5         | 5.13                          | 157                                       | -19                               | 10    | 12     | 600                                    | T1        | A   |
| TWCA226*075□LSZ0^00 |                              |                                    |                 |                   | 4.25        | 2.57                          |   |                                   |       |        |  |           |     |
| TWCB826*075□CSZ0^00 | 82                           | 75                                 | 4               | 24                | 15.2        | 2.46                          | 63  | -30                               | 12    | 15     | 1,000                                  | T2        | B   |
| TWCB826*075□LSZ0^00 |                              |                                    |                 |                   | 7.6         | 1.23                          |   |                                   |       |        |  |           |     |
| TWCD187*075□CSZ0^00 | 180                          | 75                                 | 9               | 36                | 24.4        | 2.23                          | 30  | -35                               | 16    | 20     | 1,300                                  | T3        | D   |
| TWCD187*075□LSZ0^00 |                              |                                    |                 |                   | 12.2        | 0.9                           |   |                                   |       |        |  |           |     |
| TWCE227*075□CSZ0^00 | 220                          | 75                                 | 10              | 40                | 37          | 1.8                           | 24  | -40                               | 20    | 25     | 1,800                                  | T4        | E   |
| TWCE227*075□LSZ0^00 |                              |                                    |                 |                   | 18.5        | 1.12                          |   |                                   |       |        |  |           |     |
| TWCA106*100□CSZ0^00 | 10                           | 100                                | 3               | 12                | 4.5         | 5.97                          | 200                                       | -17                               | 10    | 12     | 800                                    | T1        | A   |
| TWCA106*100□LSZ0^00 |                              |                                    |                 |                   | 2.25        | 2.99                          |   |                                   |       |        |  |           |     |
| TWCB396*100□CSZ0^00 | 39                           | 100                                | 5               | 24                | 10.4        | 3.54                          | 80  | -20                               | 12    | 15     | 1,300                                  | T2        | B   |
| TWCB396*100□LSZ0^00 |                              |                                    |                 |                   | 5.2         | 1.77                          |   |                                   |       |        |  |           |     |
| TWCD686*100□CSZ0^00 | 68                           | 100                                | 10              | 40                | 11.3        | 2.21                          | 40  | -30                               | 14    | 16     | 1,600                                  | T3        | D   |
| TWCD686*100□LSZ0^00 |                              |                                    |                 |                   | 5.65        | 1.11                          |   |                                   |       |        |  |           |     |
| TWCE127*100□CSZ0^00 | 120                          | 100                                | 12              | 48                | 25          | 2.76                          | 30  | -35                               | 15    | 17     | 2,000                                  | T4        | E   |
| TWCE127*100□LSZ0^00 |                              |                                    |                 |                   | 12.5        | 1.38                          |   |                                   |       |        |  |           |     |
| TWCB276*125□CSZ0^00 | 27                           | 125                                | 5               | 24                | 7.2         | 3.54                          | 90  | -18                               | 12    | 15     | 1,200                                  | T2        | B   |
| TWCB276*125□LSZ0^00 |                              |                                    |                 |                   | 3.6         | 1.77                          |   |                                   |       |        |  |           |     |
| TWCD476*125□CSZ0^00 | 47                           | 125                                | 10              | 40                | 7.9         | 2.23                          | 50  | -26                               | 14    | 16     | 1,500                                  | T3        | D   |
| TWCD476*125□LSZ0^00 |                              |                                    |                 |                   | 3.95        | 1.12                          |   |                                   |       |        |  |           |     |
| TWCE826*125□CSZ0^00 | 82                           | 125                                | 12              | 48                | 17.4        | 2.82                          | 32  | -30                               | 15    | 17     | 1,900                                  | T4        | E   |
| TWCE826*125□LSZ0^00 |                              |                                    |                 |                   | 8.7         | 1.41                          |   |                                   |       |        |  |           |     |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

### TESTING

All TWC COTS-Plus product is tested using MIL-PRF-39006 test procedures.

#### Lot Conformance Testing\*

| Inspection   | Sampling Procedure |
|--|--------------------|
| Constant Voltage Conditioning<br>DC Leakage<br>Capacitance<br>Dissipation Factor<br>Seal, Condition A or D | 100% Inspection    |
| Visual Examination<br><br>Material<br>Marking<br>Workmanship   | 13 Samples         |


\*Additional testing and inspection is available, please contact the factory for details.



# TWC-Y High Temperature Series



## COTS-Plus 200°C Wet Tantalum



The TWC-Y high temperature series represents a COTS-Plus version of conventional wet electrolytic tantalum capacitors that are designed for use at 200°C. The components listed are now capable of 500 hours of operation at extreme temperature with the applicable derated voltage.


This design includes a welded tantalum can and header assembly that provides a hermetic seal to withstand harsh environments.

This is a new product line so please contact the factory for availability and additional details.

### CASE DIMENSIONS: millimeters (inches)

| Standard Case Size | AVX Case Size | L<br>+0.79 (0.031)<br>-0.41 (0.016) | D<br>Basic Case<br>±0.41 (0.016) | D<br>Insulated Case<br>Max | E<br>±6.35 (0.250) |
|--------------------|---------------|-------------------------------------|----------------------------------|----------------------------|--------------------|
| T1                 | A             | 11.51 (0.453)                       | 4.78 (0.188)                     | 5.56 (0.219)               | 38.10 (1.500)      |
| T2                 | B             | 16.28 (0.641)                       | 7.14 (0.281)                     | 7.92 (0.312)               | 57.15 (2.250)      |
| T3                 | D             | 19.46 (0.766)                       | 9.52 (0.375)                     | 10.31 (0.406)              | 57.15 (2.250)      |
| T4                 | E             | 26.97 (1.062)                       | 9.52 (0.375)                     | 10.31 (0.406)              | 57.15 (2.250)      |

### OUTLINE DIMENSIONS



#### 200°C LIFE TEST:

These components are capable of 500 hours of operation at 200°C with the applicable 60% derated voltage. Following the life test components which are stabilized at 25°C ± 5°C shall exhibit:

Leakage less than 200% the original requirement or ± 10µA (whichever is greater)

ESR not greater than 200% the original requirement

Capacitance increase less than 10% or decrease less than 20% the initial measurement

### HOW TO ORDER

#### AVX PART NUMBER:

|            |           |  |   |              |  |                         |                                 |                           |   |                                      |
|------------|-----------|--|---|--------------|--|-------------------------|---------------------------------|---------------------------|---|--------------------------------------|
| <b>TWC</b> | <b>B</b>  | <b>476</b>   | <b>*</b>                                      | <b>050</b>   | <b>□</b>   | <b>C</b>                | <b>Y</b>                        | <b>Z</b>                  | <b>^</b>  | <b>00</b>                            |
| Type       | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>M = ±20%<br>K = ±10% | Voltage Code | Insulation Sleeve<br>C = Without Sleeve<br>S = With Sleeve | ESR<br>C = Standard ESR | Qualification<br>Y = High Temp. | Reliability<br>Z = Non-ER | Termination Finish<br>00 = Sn/Pb 60/40<br>07 = 100% Tin | Custom Test Options<br>00 = Standard |



### TECHNICAL SPECIFICATIONS

Technical Data: Unless otherwise specified, all technical data relate to an ambient temperature of +25°C

Capacitance Tolerance: ±10%; ±20%

|   |                 |            |            |          |          |           |           |           |           |           |           |           |
|---|-----------------|------------|------------|----------|----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| Rated Voltage (V <sub>R</sub> )           | ≤ 85°C:         | 6          | 8          | 10       | 15       | 25        | 30        | 50        | 60        | 75        | 100       | 125       |
| Category Voltage (V <sub>C</sub> )        | ≤ 125°C:        | 4          | 5          | 7        | 10       | 15        | 20        | 30        | 40        | 50        | 65        | 85        |
| <b>High Temp, Voltage (V<sub>T</sub>)</b> | <b>≤ 200°C:</b> | <b>3.6</b> | <b>4.8</b> | <b>6</b> | <b>9</b> | <b>12</b> | <b>18</b> | <b>30</b> | <b>36</b> | <b>45</b> | <b>60</b> | <b>75</b> |
| Surge Voltage (V <sub>S</sub> )           | ≤ 85°C:         | 6.9        | 9.2        | 11.5     | 17.3     | 28.8      | 34.5      | 57.5      | 69        | 86.3      | 115       | 144       |

Temperature Range: -55°C to +200°C

# TWC-Y High Temperature Series



## COTS-Plus 200°C Wet Tantalum

### STANDARD RATINGS & PART NUMBER REFERENCE

| AVX Part Number  | Cap (µF)<br>+25°C<br>at 120Hz | DC Rated<br>Voltage (V)<br>at +85°C | DC Leakage (µA) |                   | DF<br>(max) | ESR Max<br>(Ohms)<br>at 120Hz | Maximum Capacitance<br>Change (%) |       |        | Case Size |     |
|--|-------------------------------|-------------------------------------|-----------------|-------------------|-------------|-------------------------------|-----------------------------------|-------|--------|-----------|-----|
|  |                               |                                     | +25°C           | +85°C<br>& +125°C |             |                               | -55°C                             | +85°C | +125°C | Standard  | AVX |
| <b>6 VDC at 85°C    4 VDC at 125°C    3.6 VDC at 200°C</b>   |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCB147*006□CYZ0^00  | 140                           | 6                                   | 1               | 3                 | 21          | 1.99                          | -40                               | 14    | 16     | T2        | B   |
| TWCD337*006□CYZ0^00  | 330                           | 6                                   | 2               | 7.9               | 36          | 1.45                          | -44                               | 14    | 16     | T3        | D   |
| TWCD567*006□CYZ0^00  | 560                           | 6                                   | 2               | 13                | 55          | 1.30                          | -64                               | 17.5  | 20     | T3        | D   |
| <b>8 VDC at 85°C    5 VDC at 125°C    4.8 VDC at 200°C</b>   |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCB127*008□CYZ0^00  | 120                           | 8                                   | 1               | 2                 | 20          | 2.21                          | -44                               | 17.5  | 20     | T2        | B   |
| TWCD297*008□CYZ0^00  | 290                           | 8                                   | 2               | 6                 | 34          | 1.56                          | -64                               | 17.5  | 20     | T3        | D   |
| TWCD437*008□CYZ0^00  | 430                           | 8                                   | 2               | 14                | 46          | 1.42                          | -64                               | 17.5  | 20     | T3        | D   |
| <b>10 VDC at 85°C    7 VDC at 125°C    6 VDC at 200°C</b>    |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCB107*010□CYZ0^00  | 100                           | 10                                  | 1               | 4                 | 15          | 1.99                          | -36                               | 14    | 16     | T2        | B   |
| TWCD257*010□CYZ0^00  | 250                           | 10                                  | 2               | 10                | 30          | 1.59                          | -40                               | 14    | 16     | T3        | D   |
| TWCD397*010□CYZ0^00  | 390                           | 10                                  | 2               | 16                | 44          | 1.50                          | -64                               | 17.5  | 20     | T3        | D   |
| <b>15 VDC at 85°C    10 VDC at 125°C    9 VDC at 200°C</b>   |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCB706*015□CYZ0^00  | 70                            | 15                                  | 1               | 4                 | 13          | 2.46                          | -28                               | 14    | 16     | T2        | B   |
| TWCD177*015□CYZ0^00  | 170                           | 15                                  | 2               | 10                | 25          | 1.95                          | -32                               | 14    | 16     | T3        | D   |
| TWCD277*015□CYZ0^00  | 270                           | 15                                  | 2               | 16                | 32          | 1.57                          | -56                               | 17.6  | 20     | T3        | D   |
| <b>25 VDC at 85°C    15 VDC at 125°C    15 VDC at 200°C</b>  |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCA226*025□CYZ0^00  | 22                            | 25                                  | 1               | 2                 | 6.6         | 3.98                          | -20                               | 10.5  | 12     | T1        | A   |
| TWCA686*025□CYZ0^00  | 68                            | 25                                  | 2               | 9                 | 22          | 4.29                          | -50                               | 12    | 15     | T1        | A   |
| TWCB107*025□CYZ0^00  | 100                           | 25                                  | 1               | 10                | 15          | 1.99                          | -28                               | 13    | 15     | T2        | B   |
| TWCD127*025□CYZ0^00  | 120                           | 25                                  | 2               | 6                 | 21          | 2.32                          | -32                               | 13    | 15     | T3        | D   |
| TWCD187*025□CYZ0^00  | 180                           | 25                                  | 2               | 18                | 26          | 1.92                          | -48                               | 13    | 15     | T3        | D   |
| TWCB277*025□CYZ0^00  | 270                           | 25                                  | 3               | 16                | 55          | 2.70                          | -62                               | 13    | 16     | T2        | B   |
| TWCD567*025□CYZ0^00  | 560                           | 25                                  | 7               | 28                | 76          | 1.80                          | -77                               | 20    | 25     | T3        | D   |
| <b>30 VDC at 85°C    20 VDC at 125°C    18 VDC at 200°C</b>  |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCA156*030□CYZ0^00  | 15                            | 30                                  | 1               | 2                 | 5           | 4.42                          | -20                               | 10.5  | 12     | T1        | A   |
| TWCA566*030□CYZ0^00  | 56                            | 30                                  | 2               | 9                 | 22          | 5.21                          | -48                               | 12    | 15     | T1        | A   |
| TWCB686*030□CYZ0^00  | 68                            | 30                                  | 1               | 8                 | 13          | 2.54                          | -24                               | 13    | 15     | T2        | B   |
| TWCD107*030□CYZ0^00  | 100                           | 30                                  | 2               | 12                | 17          | 2.26                          | -28                               | 10.5  | 12     | T3        | D   |
| TWCD157*030□CYZ0^00  | 150                           | 30                                  | 2               | 18                | 23          | 2.03                          | -48                               | 13    | 15     | T3        | D   |
| TWCB227*030□CYZ0^00  | 220                           | 30                                  | 3               | 16                | 42          | 2.53                          | -60                               | 13    | 16     | T2        | B   |
| TWCE307*030□CYZ0^00  | 300                           | 30                                  | 8               | 32                | 31          | 1.37                          | -60                               | 25    | 25     | T4        | E   |
| TWCD397*030□CYZ0^00  | 390                           | 30                                  | 6               | 18                | 53          | 1.80                          | -65                               | 18    | 25     | T3        | D   |
| TWCD477*030□CYZ0^00  | 470                           | 30                                  | 8               | 32                | 64          | 1.81                          | -70                               | 20    | 25     | T3        | D   |
| TWCE567*030□CYZ0^00  | 560                           | 30                                  | 9               | 36                | 55          | 1.30                          | -65                               | 25    | 30     | T4        | E   |
| <b>50 VDC at 85°C    30 VDC at 125°C    30 VDC at 200°C</b>  |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCA106*050□CYZ0^00  | 10                            | 50                                  | 1               | 2                 | 4           | 5.31                          | -24                               | 8     | 9      | T1        | A   |
| TWCA336*050□CYZ0^00  | 33                            | 50                                  | 2               | 9                 | 12.3        | 4.95                          | -39                               | 10    | 12     | T1        | A   |
| TWCB476*050□CYZ0^00  | 47                            | 50                                  | 1               | 9                 | 11          | 3.11                          | -28                               | 13    | 15     | T2        | B   |
| TWCD606*050□CYZ0^00  | 60                            | 50                                  | 2               | 12                | 12          | 2.65                          | -16                               | 10.5  | 12     | T3        | D   |
| TWCD826*050□CYZ0^00  | 82                            | 50                                  | 2               | 16                | 15          | 2.43                          | -32                               | 13    | 15     | T3        | D   |
| TWCB127*050□CYZ0^00  | 120                           | 50                                  | 4               | 24                | 22.5        | 2.49                          | -42                               | 12    | 15     | T2        | B   |
| TWCE167*050□CYZ0^00  | 160                           | 50                                  | 8               | 32                | 17          | 1.41                          | -50                               | 25    | 25     | T4        | E   |
| TWCD277*050□CYZ0^00  | 270                           | 50                                  | 8               | 32                | 37          | 1.82                          | -51                               | 20    | 25     | T3        | D   |
| TWCE337*050□CYZ0^00  | 330                           | 50                                  | 9               | 36                | 38          | 1.53                          | -46                               | 25    | 30     | T4        | E   |
| <b>60V VDC at 85°C    40 VDC at 125°C    36 VDC at 200°C</b> |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCA825*060□CYZ0^00  | 8.2                           | 60                                  | 1               | 2                 | 4           | 6.47                          | -24                               | 8     | 9      | T1        | A   |
| TWCA276*060□CYZ0^00  | 27                            | 60                                  | 3               | 12                | 10.2        | 5.01                          | -34                               | 10    | 12     | T1        | A   |
| TWCD506*060□CYZ0^00  | 50                            | 60                                  | 2               | 12                | 10          | 2.65                          | -16                               | 10.5  | 12     | T3        | D   |
| TWCD686*060□CYZ0^00  | 68                            | 60                                  | 2               | 16                | 13          | 2.54                          | -32                               | 10.5  | 12     | T3        | D   |
| TWCB107*060□CYZ0^00  | 100                           | 60                                  | 4               | 20                | 19          | 2.52                          | .36                               | 12    | 15     | T2        | B   |
| TWCE147*060□CYZ0^00  | 140                           | 60                                  | 8               | 32                | 16          | 1.52                          | -40                               | 20    | 20     | T4        | E   |
| TWCD227*060□CYZ0^00  | 220                           | 60                                  | 8               | 32                | 30          | 1.81                          | -45                               | 16    | 20     | T3        | D   |
| TWCE277*060□CYZ0^00  | 270                           | 60                                  | 9               | 36                | 27          | 1.33                          | -45                               | 20    | 25     | T4        | E   |
| <b>75V VDC at 85°C    50 VDC at 125°C    45 VDC at 200°C</b> |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCA685*075□CYZ0^00  | 6.8                           | 75                                  | 1               | 2                 | 3.5         | 6.83                          | -20                               | 8     | 9      | T1        | A   |
| TWCA226*075□CYZ0^00  | 22                            | 75                                  | 3               | 12                | 8.5         | 5.13                          | -29                               | 10    | 12     | T1        | A   |
| TWCD566*075□CYZ0^00  | 56                            | 75                                  | 2               | 17                | 11          | 2.61                          | -28                               | 10.5  | 15     | T3        | D   |
| TWCB826*075□CYZ0^00  | 82                            | 75                                  | 4               | 24                | 15.2        | 2.46                          | -30                               | 12    | 15     | T2        | B   |
| TWCE117*075□CYZ0^00  | 110                           | 75                                  | 9               | 36                | 12          | 1.45                          | -35                               | 20    | 20     | T4        | E   |
| TWCD187*075□CYZ0^00  | 180                           | 75                                  | 9               | 36                | 24.4        | 2.23                          | -40                               | 16    | 20     | T3        | D   |
| TWCE227*075□CYZ0^00  | 220                           | 75                                  | 10              | 40                | 37          | 1.80                          | -40                               | 20    | 25     | T4        | E   |
| <b>100 VDC at 85°C    65 VDC at 125°C    60 VDC at 200°C</b> |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCB226*100□CYZ0^00  | 22                            | 100                                 | 1               | 9                 | 7.5         | 4.52                          | -16                               | 8     | 8      | T2        | B   |
| TWCE127*100□CYZ0^00  | 120                           | 100                                 | 12              | 48                | 25          | 2.76                          | -35                               | 15    | 17     | T4        | E   |
| <b>125 VDC at 85°C    85 VDC at 125°C    75 VDC at 200°C</b> |                               |                                     |                 |                   |             |                               |                                   |       |        |           |     |
| TWCB276*125□CYZ0^00  | 27                            | 125                                 | 5               | 24                | 7.2         | 3.54                          | -18                               | 12    | 15     | T2        | B   |
| TWCE826*125□CYZ0^00  | 82                            | 125                                 | 12              | 48                | 17.4        | 2.82                          | -30                               | 15    | 17     | T4        | E   |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes. Note: AVX reserves the right to supply higher voltage rating in the same case size to the same reliability standards.



# TWD High Temp Max Cap (HTMC) Series



## Wet Tantalum Super Capacitor



The TWD series is an axial leaded wet electrolytic tantalum capacitor designed for DC (hold-up) and low frequency pulse applications.

Utilizing high CV Tantalum powders the HTMC series achieves extreme high capacitance values that are similar to the Super capacitor range. The HTMC offers extended temperature range up to 125°C and extended life up to 10000 hrs.

Components are suitable for automatic mounting and soldering.

Well-established wet tantalum design is suitable for applications with hi-reliability requirements. Contact the factory about design possibilities beyond those contained in this datasheet.


### FEATURES

- Super high capacitance
- -55 to 125°C operation temperature
- Hermetic packaging
- Endurance up to 10 000 hrs. on selected codes
- High electrical and mechanical stability

### APPLICATIONS

- Special industrial
- Avionics
- Military

### OUTLINE DIMENSIONS



### CASE DIMENSIONS: millimeters (inches)

| DSCC Case Size | AVX Case Size | L                              | D                         |                            | E             |
|----------------|---------------|--------------------------------|---------------------------|----------------------------|---------------|
|                |               |                                | Without Insulating Sleeve | With Insulating Sleeve Max |               |
| T4             | E             | +0.79 (0.031)<br>-0.41 (0.016) | ±0.41 (0.016)             | 10.31 (0.406)              | ±6.35 (0.250) |
|                |               | 26.97 (1.062)                  | 9.52 (0.375)              |                            | 57.15 (2.250) |

### CAPACITANCE AND RATED VOLTAGE, $V_R$ (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| DC Capacitance |      | Rated Voltage DC ( $V_R$ ) to 85°C |      |     |
|----------------|------|------------------------------------|------|-----|
| mF             | Code | 2.5V                               | 6.3V | 10V |
| 25             | 253  |                                    |      | E   |
| 50             | 503  |                                    | E    |     |
| 150            | 154  |                                    |      |     |

Available Ratings

# TWD High Temp Max Cap (HTMC) Series



## Wet Tantalum Super Capacitor

### HOW TO ORDER

#### AVX PART NUMBER:

|            |           |  |   |   |  |                            |                             |                           |                                |  |                                      |
|------------|-----------|--|---|---|--|----------------------------|-----------------------------|---------------------------|--------------------------------|--|--------------------------------------|
| <b>TWD</b> | <b>E</b>  | <b>503</b>   | <b>*</b>                                      | <b>006</b>  | <b>□</b>   | <b>B</b>                   | <b>0</b>                    | <b>Z</b>                  | <b>0</b>                       | <b>^</b>   | <b>00</b>                            |
| Type       | Case Size | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Capacitance Tolerance<br>K = ±10%<br>M = ±20% | Voltage Code<br>002 = 2.5Vdc<br>006 = 6.3Vdc<br>010 = 10Vdc | Insulation Sleeve<br>C = Without Sleeve<br>S = With Sleeve | Packaging<br>B = Tray Pack | Inspection Level<br>0 = N/A | Reliability<br>Z = Non-ER | Qualification Level<br>0 = N/A | Termination Finish<br>0 = Sn/Pb 60/40<br>7 = Matte tin | Custom Test Options<br>00 = Standard |




### TECHNICAL SPECIFICATIONS

|                                    |   |                                |     |      |  |
|------------------------------------|---|--------------------------------|-----|------|--|
| Technical Data:                    | All technical data relate to an ambient temperature of +25°C                                |                                |     |      |  |
| Capacitance Range:                 | 25mF to 50mF (for extended range under development, contact manufacturer)                   |                                |     |      |  |
| Capacitance Tolerance:             | ±10%; ±20%  |                                |     |      |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ 85°C:   | 2.5                            | 6.3 | 10   |  |
| Category Voltage (V <sub>C</sub> ) | ≤ 125°C:  | n/a                            | 4.2 | 6.6  |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ 85°C:   | 2.5                            | 7.2 | 11.5 |  |
| Temperature Range:                 | -55°C to +85°C  | -55°C to +125°C                |     |      |  |
| Endurance:                         | 2000h at +85°C/V <sub>R</sub>   | 10000h at +85°C/V <sub>R</sub> |     |      |  |
| Reliability:                       | 1% per 1000 hours at 85°C, V <sub>R</sub> with 0.1Ω/Vseries impedance, 60% confidence level |                                |     |      |  |
| Termination Finish:                | Sn Plating, SnPb Plating 60/40  |                                |     |      |  |

### RATINGS & PART NUMBER REFERENCE

| AVX Part Number        | Cap (mF) <sup>2/</sup> at 25°C | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DC Leakage Max (μA) <sup>1/</sup> |       |        | Maximum Capacitance Change (%) |       |        | ESR Max (mOhms) at 1kHz | Case Size |      | Lifetime at 85°C (hrs.) |  |
|------------------------|--------------------------------|-------------------|------------------------|----------------------|---------------------------|-----------------------------------|-------|--------|--------------------------------|-------|--------|-------------------------|-----------|------|-------------------------|--|
|                        |                                |                   |                        |                      |                           | +25°C                             | +85°C | +125°C | -55°C                          | +85°C | +125°C |                         | AVX       | DSCC |                         |  |
| <b>6.3 VDC at 85°C</b> |                                |                   |                        |                      |                           |                                   |       |        |                                |       |        |                         |           |      |                         |  |
| TWDE503*006□B0Z0^00    | 50                             | 6.3               | 85                     | 4.16                 | 125                       | 20                                | 60    | 60     | -15                            | +20   | +30    | 400                     | E         | T4   | 10000                   |  |
| <b>10 VDC at 85°C</b>  |                                |                   |                        |                      |                           |                                   |       |        |                                |       |        |                         |           |      |                         |  |
| TWDE253*010□B0Z0^00    | 25                             | 10                | 85                     | 6.6                  | 125                       | 20                                | 60    | 60     | -15                            | +20   | +30    | 400                     | E         | T4   | 10000                   |  |

- 1/ DCL is measured at rated or category voltage after 20 minutes.
- 2/ DC capacitance is measured by discharging initially fully charged capacitor down to 0.37U<sub>r</sub> through 1kOhm.





## HOW TO ORDER

### AVX PART NUMBER:

|           |           |  |                       |            |          |           |               |                         |                   |                    |               |
|-----------|-----------|--|-----------------------|------------|----------|-----------|---------------|-------------------------|-------------------|--------------------|---------------|
| <b>TW</b> | <b>2E</b> | <b>227</b>   | <b>*</b>              | <b>050</b> | <b>C</b> | <b>B</b>  | <b>@</b>      | <b>Z</b>                | <b>0</b>          | <b>S</b>           | <b>++</b>     |
| Type      | Case Size | Capacitance Code   | Capacitance Tolerance | Voltage    | C = N/A  | Packaging | Qualification | Established Reliability | Reliability Grade | Termination Finish | Special Code  |
|           |           | pF code:<br>1st two digits represent significant figures<br>3rd digit represents multiplier<br>(number of zeros to follow) | K = ±10%<br>M = ±20%  |            |          | B = Bulk  | S = COTS-PLus | Z = Non-ER              | 0 = Standard      | S = Silver Plating | 00 = Standard |

**Not RoHS Compliant**

*SnPb termination option is not RoHS compliant.*

## RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage<sup>1/2/</sup>

| Frequency of Applied Ripple Current | 120Hz   |      |      |      | 800Hz |      |      |      | 1kHz |      |      |      |      |
|-------------------------------------|---------|------|------|------|-------|------|------|------|------|------|------|------|------|
|                                     | ≤55     | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55  | 85   | 105  | 125  |      |
| % of 85°C                           | 100%    | 0.60 | 0.39 | –    | –     | 0.71 | 0.43 | –    | –    | 0.72 | 0.45 | –    | –    |
| Rated Peak Voltage                  | 90%     | 0.60 | 0.46 | –    | –     | 0.71 | 0.55 | –    | –    | 0.72 | 0.55 | –    | –    |
|                                     | 80%     | 0.60 | 0.52 | 0.35 | –     | 0.71 | 0.62 | 0.42 | –    | 0.72 | 0.62 | 0.42 | –    |
|                                     | 70%     | 0.60 | 0.58 | 0.44 | –     | 0.71 | 0.69 | 0.52 | –    | 0.72 | 0.70 | 0.52 | –    |
|                                     | 66-2/3% | 0.60 | 0.60 | 0.46 | 0.27  | 0.71 | 0.71 | 0.55 | 0.32 | 0.72 | 0.72 | 0.55 | 0.32 |

| Frequency of Applied Ripple Current | 10kHz   |      |      |      | 40kHz |      |      |      | 100kHz |      |      |      |      |
|-------------------------------------|---------|------|------|------|-------|------|------|------|--------|------|------|------|------|
|                                     | ≤55     | 85   | 105  | 125  | ≤55   | 85   | 105  | 125  | ≤55    | 85   | 105  | 125  |      |
| % of 85°C                           | 100%    | 0.88 | 0.55 | –    | –     | 1.00 | 0.63 | –    | –      | 1.10 | 0.69 | –    | –    |
| Rated Peak Voltage                  | 90%     | 0.88 | 0.67 | –    | –     | 1.00 | 0.77 | –    | –      | 1.10 | 0.85 | –    | –    |
|                                     | 80%     | 0.88 | 0.76 | 0.52 | –     | 1.00 | 0.87 | 0.59 | –      | 1.10 | 0.96 | 0.65 | –    |
|                                     | 70%     | 0.88 | 0.85 | 0.64 | –     | 1.00 | 0.97 | 0.73 | –      | 1.10 | 1.07 | 0.80 | –    |
|                                     | 66-2/3% | 0.88 | 0.88 | 0.68 | 0.40  | 1.00 | 1.00 | 0.77 | 0.45   | 1.10 | 1.10 | 0.85 | 0.50 |

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.

## RATINGS & PART NUMBER REFERENCE

| AVX Part Number                        | Cap (uF)      | DC Rated Voltage (V) | ESR Max (ohms) | DC Leakage Max (uA) |                | Max Impedance (Ohms) | Maximum Capacitance Change* (%) |       |        | Max AC Ripple* (mA rms) |
|--|---------------|----------------------|----------------|---------------------|----------------|----------------------|---------------------------------|-------|--------|-------------------------|
|  | 25°C at 120Hz | 85°C                 | 120Hz          | +25°C               | +85 and +125°C | -55°C at 120 Hz      | -55°C                           | +85°C | +125°C | 85°C at 40kHz           |
| <b>25 VDC at 85°C 15 VDC at 125°C</b>  |               |                      |                |                     |                |                      |                                 |       |        |                         |
| TW2D248*025CB@Z0S++                    | 2400          | 25                   | 0.33           | 10                  | 40             | 3.50                 | -70                             | 12    | 18     | 5200                    |
| TW3D368*025CB@Z0S++                    | 3600          | 25                   | 0.22           | 15                  | 60             | 2.33                 | -70                             | 12    | 18     | 7800                    |
| TW2E368*025CB@Z0S++                    | 3600          | 25                   | 0.25           | 12                  | 50             | 3.50                 | -75                             | 12    | 20     | 6200                    |
| TW2E448*025CB@Z0S++                    | 4400          | 25                   | 0.25           | 20                  | 160            | 5.00                 | -90                             | 30    | 50     | 6400                    |
| TW3E548*025CB@Z0S++                    | 5400          | 25                   | 0.17           | 18                  | 75             | 2.33                 | -75                             | 12    | 20     | 9300                    |
| TW3E668*025CB@Z0S++                    | 6600          | 25                   | 0.17           | 30                  | 240            | 3.33                 | -90                             | 30    | 50     | 9600                    |
| <b>30 VDC at 85°C 20 VDC at 125°C</b>  |               |                      |                |                     |                |                      |                                 |       |        |                         |
| TW2D208*030CB@Z0S++                    | 2000          | 30                   | 0.35           | 14                  | 50             | 3.50                 | -70                             | 10    | 18     | 5000                    |
| TW3D308*030CB@Z0S++                    | 3000          | 30                   | 0.23           | 21                  | 75             | 2.33                 | -70                             | 10    | 18     | 7500                    |
| TW2E308*030CB@Z0S++                    | 3000          | 30                   | 0.30           | 24                  | 70             | 3.00                 | -72                             | 10    | 20     | 6000                    |
| TW3E458*030CB@Z0S++                    | 4500          | 30                   | 0.20           | 36                  | 105            | 2.00                 | -72                             | 10    | 20     | 9000                    |
| <b>50 VDC at 85°C 30 VDC at 125°C</b>  |               |                      |                |                     |                |                      |                                 |       |        |                         |
| TW2D947*050CB@Z0S++                    | 940           | 50                   | 0.38           | 6                   | 50             | 5.00                 | -50                             | 8     | 15     | 4200                    |
| TW2E148*050CB@Z0S++                    | 1360          | 50                   | 0.35           | 10                  | 80             | 4.00                 | -58                             | 10    | 20     | 5500                    |
| TW3D148*050CB@Z0S++                    | 1410          | 50                   | 0.25           | 9                   | 75             | 3.33                 | -50                             | 8     | 15     | 6300                    |
| TW3E208*050CB@Z0S++                    | 2040          | 50                   | 0.23           | 15                  | 120            | 2.67                 | -58                             | 10    | 20     | 8250                    |
| TW2E308*050CB@Z0S++                    | 3000          | 50                   | 0.50           | 38                  | 200            | 7.50                 | -90                             | 25    | 35     | 6000                    |
| TW3E458*050CB@Z0S++                    | 4500          | 50                   | 0.33           | 57                  | 300            | 5.00                 | -90                             | 25    | 35     | 9000                    |
| TW3E908*050CB@Z0S++                    | 9000          | 50                   | 0.33           | 150                 | 450            | 1.20                 | -80                             | 60    | 85     | 9300                    |
| <b>60 VDC at 85°C 40 VDC at 125°C</b>  |               |                      |                |                     |                |                      |                                 |       |        |                         |
| TW2D787*060CB@Z0S++                    | 780           | 60                   | 0.45           | 6                   | 50             | 7.50                 | -60                             | 8     | 15     | 4200                    |
| TW2E118*060CB@Z0S++                    | 1120          | 60                   | 0.40           | 10                  | 80             | 5.00                 | -58                             | 8     | 15     | 5500                    |
| TW3D128*060CB@Z0S++                    | 1170          | 60                   | 0.30           | 9                   | 75             | 5.00                 | -60                             | 8     | 15     | 6300                    |
| TW3E178*060CB@Z0S++                    | 1680          | 60                   | 0.27           | 15                  | 120            | 3.33                 | -58                             | 8     | 15     | 8250                    |
| TW2E208*060CB@Z0S++                    | 2000          | 60                   | 0.50           | 24                  | 180            | 10.00                | -90                             | 30    | 50     | 6400                    |
| TW3E308*060CB@Z0S++                    | 3000          | 60                   | 0.33           | 36                  | 270            | 6.67                 | -90                             | 30    | 50     | 9600                    |
| <b>75 VDC at 85°C 50 VDC at 125°C</b>  |               |                      |                |                     |                |                      |                                 |       |        |                         |
| TW2D667*075CB@Z0S++                    | 660           | 75                   | 0.50           | 6                   | 60             | 6.00                 | -45                             | 6     | 10     | 4200                    |
| TW2E947*075CB@Z0S++                    | 940           | 75                   | 0.45           | 10                  | 100            | 6.00                 | -55                             | 6     | 10     | 5500                    |
| TW3D997*075CB@Z0S++                    | 990           | 75                   | 0.33           | 9                   | 90             | 4.00                 | -45                             | 6     | 10     | 6300                    |
| TW3E148*075CB@Z0S++                    | 1410          | 75                   | 0.30           | 15                  | 150            | 4.00                 | -55                             | 6     | 10     | 8250                    |
| <b>100 VDC at 85°C 65 VDC at 125°C</b> |               |                      |                |                     |                |                      |                                 |       |        |                         |
| TW2D307*100CB@Z0S++                    | 300           | 100                  | 0.80           | 6                   | 50             | 11.00                | -35                             | 6     | 12     | 4200                    |
| TW2E447*100CB@Z0S++                    | 440           | 100                  | 0.60           | 10                  | 100            | 7.50                 | -40                             | 6     | 12     | 5500                    |
| TW3D457*100CB@Z0S++                    | 450           | 100                  | 0.53           | 9                   | 75             | 7.33                 | -35                             | 6     | 12     | 6300                    |
| TW3E667*100CB@Z0S++                    | 660           | 100                  | 0.40           | 15                  | 150            | 5.00                 | -40                             | 6     | 12     | 8250                    |
| <b>125 VDC at 85°C 85 VDC at 125°C</b> |               |                      |                |                     |                |                      |                                 |       |        |                         |
| TW2D207*125CB@Z0S++                    | 200           | 125                  | 0.90           | 6                   | 50             | 17.50                | -35                             | 5     | 12     | 4200                    |
| TW3D307*125CB@Z0S++                    | 300           | 125                  | 0.60           | 9                   | 75             | 11.67                | -35                             | 5     | 12     | 6300                    |
| TW2E307*125CB@Z0S++                    | 300           | 125                  | 0.80           | 10                  | 100            | 10.00                | -35                             | 6     | 12     | 5500                    |
| TW3E457*125CB@Z0S++                    | 450           | 125                  | 0.53           | 15                  | 150            | 6.67                 | -35                             | 6     | 12     | 8250                    |

\*For reference only, contact factory for more details

# TAJ ESCC Tantalum Capacitors



## SMD Solid Tantalum Chip Capacitors




Capacitors, Fixed, Leadless Surface Mount, Chip, Solid electrolyte Tantalum for use in ESCC space programs, according to ESCC Generic Specification 3012 and associated Detail Specification 3012/001 as recommended by the Space Components Coordination Group (ranges in table below).



### CASE DIMENSIONS: millimeters (inches)


| Code | EIA Code | Variant | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|---------|----------------|------------------------------|------------------------------|------------------------------|------------------------------|--------------|
| A    | 3216-18  | 01      | 3.20 (0.126)   | 1.60 (0.063)                 | 1.60 (0.063)                 | 1.20 (0.047)                 | 0.80 (0.031)                 | 1.10 (0.043) |
| B    | 3528-21  | 02      | 3.50 (0.138)   | 2.80 (0.110)                 | 1.90 (0.075)                 | 2.20 (0.087)                 | 0.80 (0.031)                 | 1.40 (0.055) |
| C    | 6032-28  | 13      | 6.00 (0.236)   | 3.20 (0.126)                 | 2.60 (0.102)                 | 2.20 (0.087)                 | 1.30 (0.051)                 | 2.90 (0.114) |
| D    | 7343-31  | 14      | 7.30 (0.287)   | 4.30 (0.169)                 | 2.90 (0.114)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| E    | 7343-43  | 17      | 7.30 (0.287)   | 4.30 (0.169)                 | 4.10 (0.162)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.




### MARKING

#### A, B, C, D, E CASE




### HOW TO ORDER

#### AVX PART NUMBER:



#### ESCC PART NUMBER – MANDATORY FOR ORDERING:





# TAJ ESCC Tantalum Capacitors



## SMD Solid Tantalum Chip Capacitors

### CAPACITANCE AND RATED VOLTAGE, $V_R$ (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance   |      | Rated Voltage DC ( $V_R$ ) at 85°C |          |         |         |         |         |         |         |
|---------------|------|------------------------------------|----------|---------|---------|---------|---------|---------|---------|
| $\mu\text{F}$ | Code | 4V (G)                             | 6.3V (J) | 10V (A) | 16V (C) | 20V (D) | 25V (E) | 35V (V) | 50V (T) |
| 0.10          | 104  |                                    |          |         |         |         |         | A       | A       |
| 0.15          | 154  |                                    |          |         |         |         |         | A       | B       |
| 0.22          | 224  |                                    |          |         |         |         |         | A       | B       |
| 0.33          | 334  |                                    |          |         |         |         |         | A       | B       |
| 0.47          | 474  |                                    |          |         |         |         | A       | A/B     | C       |
| 0.68          | 684  |                                    |          |         |         | A       | A       | A/B     | C       |
| 1.0           | 105  |                                    |          |         | A       | A       | A       | B       | C       |
| 1.5           | 155  |                                    |          | A       | A       | A       | B       | B/C     | D       |
| 2.2           | 225  |                                    | A        | A       | A/B     | B       | B       | B/C     | D       |
| 3.3           | 335  | A                                  | A        | A       | A/B     | B       | B/C     | C       | D       |
| 4.7           | 475  | A                                  | A        | A/B     | B       | B/C     | C       | C/D     | D       |
| 6.8           | 685  | A                                  | A/B      | B       | B/C     | C       | C/D     | D       |         |
| 10            | 106  | A/B                                | B        | B/C     | C       | C       | C/D     | D       |         |
| 15            | 156  | B                                  | B/C      | C       | C       | C/D     | D       | D       |         |
| 22            | 226  | B/C                                | C        | C       | C/D     | D       | D       | E       |         |
| 33            | 336  | C                                  | C        | C/D     | D       | D       | E       |         |         |
| 47            | 476  | C/D                                | C/D      | D       | D       | E       |         |         |         |
| 68            | 686  | C/D                                | D        | D       | D       | E       |         |         |         |
| 100           | 107  | D                                  | D        | D       | E       |         |         |         |         |
| 150           | 157  | D                                  | D        | E       |         |         |         |         |         |
| 220           | 227  | E                                  | E        | E       |         |         |         |         |         |

### LAT TESTING

AVX can perform the following Lot Acceptance Test according to ESCC

- LAT 3 Qty. 10 pcs. - 4 pieces of which are “destructive samples”, the remaining 6 pieces may be for part of the Order Qty. OR be additional to the order Qty.
- LAT 2 Qty. 26 pcs. - including the 10 pieces of LAT3. The additional 16 pieces are “destructive samples”.
- LAT 1 Qty. 34 pcs. - including the 26 pieces of LAT2. The additional 8 pieces are all “destructive samples”.

### OPTION

Packaging: Tape and reel available on request – Contact marketing.

# TES Low ESR – QPL ESCC




## Low ESR Tantalum Chip Capacitor



- QPL ESCC approved series
- Manufactured in EU, ESA qualified plant, according to ESCC 3012
- Detailed specification 3012/004
- Low ESR designed parts, multianode D and E case included
- Robust against higher thermo-mechanical stresses during assembly process
- CV range 1.0 - 470uF/6.3 - 50V
- Improved reliability design



For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)




### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | Variant | L±0.20 (0.008) | W+0.20 (0.008) -0.10 (0.004) | H+0.20 (0.008) -0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012) -0.20 (0.008) | S Min.       |
|------|----------|---------|----------------|------------------------------|------------------------------|------------------------------|------------------------------|--------------|
| A    | 3216-18  | 01      | 3.20 (0.126)   | 1.60 (0.063)                 | 1.60 (0.063)                 | 1.20 (0.047)                 | 0.80 (0.031)                 | 1.10 (0.043) |
| B    | 3528-21  | 02      | 3.50 (0.138)   | 2.80 (0.110)                 | 1.90 (0.075)                 | 2.20 (0.087)                 | 0.80 (0.031)                 | 1.40 (0.055) |
| C    | 6032-28  | 03      | 6.00 (0.236)   | 3.20 (0.126)                 | 2.60 (0.102)                 | 2.20 (0.087)                 | 1.30 (0.051)                 | 2.90 (0.114) |
| D    | 7343-31  | 04      | 7.30 (0.287)   | 4.30 (0.169)                 | 2.90 (0.114)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |
| E    | 7343-43  | 05      | 7.30 (0.287)   | 4.30 (0.169)                 | 4.10 (0.162)                 | 2.40 (0.094)                 | 1.30 (0.051)                 | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.

### MARKING

#### A, B, C, D, E CASE



### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) at 85°C |         |         |                |         |                |                   |                   |
|-------------|------|--|---------|---------|----------------|---------|----------------|-------------------|-------------------|
| µF          | Code | 6.3V (J)                                   | 10V (A) | 12V (B) | 16V (C)        | 20V (D) | 25V (E)        | 35V (V)           | 50V (T)           |
| 1.0         | 105  |  |         |         |                |         | A(3000)        |                   | B(2000)           |
| 1.5         | 155  |  |         |         |                |         |                |                   |                   |
| 2.2         | 225  |  |         |         |                |         |                |                   |                   |
| 3.3         | 335  |  |         |         |                |         |                |                   |                   |
| 4.7         | 475  |  |         |         | A(2000)        | A(2500) | B(1000)        | B(1000)<br>C(600) | C(1000)<br>D(200) |
| 6.8         | 685  |  |         |         |                |         |                |                   |                   |
| 10          | 106  |  | A(1800) |         |                | B(1000) | C(600)         | D(120)            |                   |
| 15          | 156  |  |         |         |                |         |                |                   |                   |
| 22          | 226  | A(900)                                     |         |         | B(600)         | C(400)  |                | D(100)            |                   |
| 33          | 336  |  | B(650)  |         |                | C(300)  | D(65)<br>E(65) | E(65)             |                   |
| 47          | 476  | B(500)                                     |         |         | C(350)         | D(55)   |                |                   |                   |
| 68          | 686  |  |         |         |                |         |                |                   |                   |
| 100         | 107  |  | C(200)  |         | D(55)<br>E(40) | E(45)   |                |                   |                   |
| 150         | 157  | C(300)                                     | D(45)   |         |                |         |                |                   |                   |
| 220         | 227  |  | D(35)   | E(35)   |                |         |                |                   |                   |
| 330         | 337  | D(35)                                      | E(35)   |         |                |         |                |                   |                   |
| 470         | 477  | E(30)                                      |         |         |                |         |                |                   |                   |

Available Ratings: ESR limits quoted in brackets (mOhms)

# TES Low ESR – QPL ESCC



## Low ESR Tantalum Chip Capacitor

### HOW TO ORDER

#### AVX PART NUMBER:

|             |                                     |   |  |  |   |   |   |   |                                   |                           |
|-------------|-------------------------------------|---|--|--|---|---|---|---|-----------------------------------|---------------------------|
| <b>TES</b>  | <b>E</b>                            | <b>477</b>  | <b>K</b>                                 | <b>006</b>   |   | <b>U</b>  | <b>0</b>  | <b>@</b>  | <b>^</b>                          | <b>Not RoHS Compliant</b> |
| <b>Type</b> | <b>Case Size</b><br>See table above | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Tolerance</b><br>K = ±10%<br>M = ±20% | <b>Voltage Code</b><br>006 = 6.3Vdc<br>010 = 10Vdc<br>012 = 12Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Packaging SnPb Termination</b><br>X = 4"<br>E = Bulk<br>H = 7" | <b>ESR Level</b><br>C = Standard<br>L = Mirror Multianode<br>U = Multianode | <b>LAT</b><br>0 = N/A<br>1 = LAT1<br>2 = LAT2<br>3 = LAT3 | <b>Screening Level</b><br>B = Level B (Xray)<br>C = Level C<br>Z = non-ER<br>(not for flight parts) | <b>FCSI</b><br>0 = N/A<br>1 = YES |                           |

#### ESCC PART NUMBER – MANDATORY FOR ORDERING:

|                             |  |   |   |  |   |                  |             |                           |
|-----------------------------|--|---|---|--|---|------------------|-------------|---------------------------|
| <b>3012</b>                 | <b>004</b>                                   | <b>01</b>   | <b>B</b>  | <b>477</b>                               | <b>K</b>  | <b>E</b>         | <b>0030</b> | <b>Not RoHS Compliant</b> |
| <b>Detail Specification</b> | <b>Variant</b><br>01<br>02<br>03<br>04<br>05 | <b>Testing Level</b><br>B = Level B (Xray)<br>C = Level C | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Tolerance</b><br>K = ±10%<br>M = ±20% | <b>Voltage</b><br>J = 6.3V<br>A = 10V<br>B = 12V<br>C = 16V<br>D = 20V<br>E = 25V<br>V = 35V<br>T = 50V | <b>ESR in mΩ</b> |             |                           |

### LAT TESTING

AVX can perform the following Lot Acceptance Test according to ESCC

- LAT 3 Qty. 10 pcs. - 4 pieces of which are “destructive samples”, the remaining 6 pieces may be for part of the Order Qty. OR be additional to the order Qty.
- LAT 2 Qty. 26 pcs. - including the 10 pieces of LAT3. The additional 16 pieces are “destructive samples”.
- LAT 1 Qty. 34 pcs. - including the 26 pieces of LAT2. The additional 8 pieces are all “destructive samples”.

### OPTION

Packaging: Tape and reel available on request – Contact marketing.

# TES Low ESR – QPL ESCC



## Low ESR Tantalum Chip Capacitor

### RATINGS & PART NUMBER REFERENCE

| ESCC Part Number                        | AVX Part Number           | Case Size | Cap (µF) | Rated Voltage (V) | DCL Max. (µA) | DF Max. (%) | ESR Max. @100kHz (mΩ) | 100kHz RMS Current (mA) |      |       | 100kHz RMS Voltage (mV) |      |       |
|---|---------------------------|-----------|----------|-------------------|---------------|-------------|-----------------------|-------------------------|------|-------|-------------------------|------|-------|
|   |                           |           |          |                   |               |             |                       | 25°C                    | 85°C | 125°C | 25°C                    | 85°C | 125°C |
| <b>6.3 Volt @ 85°C (4 Volt @ 125°C)</b> |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200401#226*J0900                     | TES A 226 * 006 □ C 0 @ ^ | A         | 22       | 6.3               | 1.32          | 6           | 900                   | 289                     | 260  | 115   | 260                     | 234  | 104   |
| 301200402#476*J0500                     | TES B 476 * 006 □ C 0 @ ^ | B         | 47       | 6.3               | 2.82          | 6           | 500                   | 412                     | 371  | 165   | 206                     | 186  | 82    |
| 301200403#157*J0300                     | TES C 157 * 006 □ C 0 @ ^ | C         | 150      | 6.3               | 9             | 6           | 300                   | 606                     | 545  | 242   | 182                     | 163  | 73    |
| 301200404#337*J0035                     | TES D 337 * 006 □ L 0 @ ^ | D         | 330      | 6.3               | 19.8          | 8           | 35                    | 2699                    | 2429 | 1080  | 94                      | 85   | 38    |
| 301200405#477*J0030                     | TES E 477 * 006 □ U 0 @ ^ | E         | 470      | 6.3               | 28.2          | 6           | 30                    | 3000                    | 2700 | 1200  | 90                      | 81   | 36    |
| <b>10 Volt @ 85°C (7 Volt @ 125°C)</b>  |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200401#106*A1800                     | TES A 106 * 010 □ C 0 @ ^ | A         | 10       | 10                | 1             | 6           | 1800                  | 204                     | 184  | 82    | 367                     | 331  | 147   |
| 301200402#336*A0650                     | TES B 336 * 010 □ C 0 @ ^ | B         | 33       | 10                | 3.3           | 6           | 650                   | 362                     | 325  | 145   | 235                     | 212  | 94    |
| 301200403#107*A0200                     | TES C 107 * 010 □ C 0 @ ^ | C         | 100      | 10                | 10            | 6           | 200                   | 742                     | 667  | 297   | 148                     | 133  | 59    |
| 301200404#157*A0045                     | TES D 157 * 010 □ L 0 @ ^ | D         | 150      | 10                | 15            | 6           | 45                    | 2380                    | 2142 | 952   | 107                     | 96   | 43    |
| 301200404#227*A0035                     | TES D 227 * 010 □ L 0 @ ^ | D         | 220      | 10                | 22            | 6           | 35                    | 2699                    | 2429 | 1080  | 94                      | 85   | 38    |
| 301200405#337*A0035                     | TES E 337 * 010 □ U 0 @ ^ | E         | 330      | 10                | 33            | 6           | 35                    | 2777                    | 2500 | 1111  | 97                      | 87   | 39    |
| <b>12 Volt @ 85°C (8 Volt @ 125°C)</b>  |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200405#227*B0035                     | TES E 227 * 012 □ U 0 @ ^ | E         | 220      | 12                | 26.4          | 6           | 35                    | 2777                    | 2500 | 1111  | 97                      | 87   | 39    |
| <b>16 Volt @ 85°C (10 Volt @ 125°C)</b> |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200401#475*C2000                     | TES A 475 * 016 □ C 0 @ ^ | A         | 4.7      | 16                | 0.75          | 6           | 2000                  | 194                     | 174  | 77    | 387                     | 349  | 155   |
| 301200402#226*C0600                     | TES B 226 * 016 □ C 0 @ ^ | B         | 22       | 16                | 3.52          | 6           | 600                   | 376                     | 339  | 151   | 226                     | 203  | 90    |
| 301200403#476*C0350                     | TES C 476 * 016 □ C 0 @ ^ | C         | 47       | 16                | 7.52          | 6           | 350                   | 561                     | 505  | 224   | 196                     | 177  | 78    |
| 301200404#107*C0055                     | TES D 107 * 016 □ L 0 @ ^ | D         | 100      | 16                | 16            | 6           | 55                    | 2153                    | 1938 | 861   | 118                     | 107  | 47    |
| 301200405#157*C0040                     | TES E 157 * 016 □ U 0 @ ^ | E         | 150      | 16                | 24            | 6           | 40                    | 2598                    | 2338 | 1039  | 104                     | 94   | 42    |
| <b>20 Volt @ 85°C (13 Volt @ 125°C)</b> |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200401#335*D2500                     | TES A 335 * 020 □ C 0 @ ^ | A         | 3.3      | 20                | 0.66          | 6           | 2500                  | 173                     | 156  | 69    | 433                     | 390  | 173   |
| 301200402#106*D1000                     | TES B 106 * 020 □ C 0 @ ^ | B         | 10       | 20                | 2             | 6           | 1000                  | 292                     | 262  | 117   | 292                     | 262  | 117   |
| 301200403#226*D0400                     | TES C 226 * 020 □ C 0 @ ^ | C         | 22       | 20                | 4.4           | 6           | 400                   | 524                     | 472  | 210   | 210                     | 189  | 84    |
| 301200403#336*D0300                     | TES C 336 * 020 □ C 0 @ ^ | C         | 33       | 20                | 6.6           | 6           | 300                   | 606                     | 545  | 242   | 182                     | 163  | 73    |
| 301200404#476*D0055                     | TES D 476 * 020 □ L 0 @ ^ | D         | 47       | 20                | 9.4           | 6           | 55                    | 2153                    | 1938 | 861   | 118                     | 107  | 47    |
| 301200405#107*D0045                     | TES E 107 * 020 □ U 0 @ ^ | E         | 100      | 20                | 20            | 6           | 45                    | 2449                    | 2205 | 980   | 110                     | 99   | 44    |
| <b>25 Volt @ 85°C (17 Volt @ 125°C)</b> |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200401#105*E3000                     | TES A 105 * 025 □ C 0 @ ^ | A         | 1.0      | 25                | 0.25          | 6           | 3000                  | 158                     | 142  | 63    | 474                     | 427  | 190   |
| 301200402#475*E1000                     | TES B 475 * 025 □ C 0 @ ^ | B         | 4.7      | 25                | 1.18          | 6           | 1000                  | 292                     | 262  | 117   | 292                     | 262  | 117   |
| 301200403#106*E0600                     | TES C 106 * 025 □ C 0 @ ^ | C         | 10       | 25                | 2.5           | 6           | 600                   | 428                     | 385  | 171   | 257                     | 231  | 103   |
| 301200404#336*E0065                     | TES D 336 * 025 □ L 0 @ ^ | D         | 33       | 25                | 8.25          | 6           | 65                    | 1981                    | 1783 | 792   | 129                     | 116  | 51    |
| 301200405#476*E0065                     | TES E 476 * 025 □ U 0 @ ^ | E         | 47       | 25                | 11.8          | 6           | 65                    | 2038                    | 1834 | 815   | 132                     | 119  | 53    |
| <b>35 Volt @ 85°C (23 Volt @ 125°C)</b> |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200402#335*V1000                     | TES B 335 * 035 □ C 0 @ ^ | B         | 3.3      | 35                | 1.16          | 6           | 1000                  | 292                     | 262  | 117   | 292                     | 262  | 117   |
| 301200403#475*V0600                     | TES C 475 * 035 □ C 0 @ ^ | C         | 4.7      | 35                | 1.65          | 6           | 600                   | 428                     | 385  | 171   | 257                     | 231  | 103   |
| 301200404#106*V0120                     | TES D 106 * 035 □ L 0 @ ^ | D         | 10       | 35                | 3.5           | 6           | 120                   | 1458                    | 1312 | 583   | 175                     | 157  | 70    |
| 301200404#226*V0100                     | TES D 226 * 035 □ L 0 @ ^ | D         | 22       | 35                | 7.7           | 6           | 100                   | 1597                    | 1437 | 639   | 160                     | 144  | 64    |
| 301200405#336*V0065                     | TES E 336 * 035 □ U 0 @ ^ | E         | 33       | 35                | 11.6          | 6           | 65                    | 2038                    | 1834 | 815   | 132                     | 119  | 53    |
| <b>50 Volt @ 85°C (33 Volt @ 125°C)</b> |                           |           |          |                   |               |             |                       |                         |      |       |                         |      |       |
| 301200402#105*T2000                     | TES B 105 * 050 □ C 0 @ ^ | B         | 1.0      | 50                | 0.5           | 6           | 2000                  | 206                     | 186  | 82    | 412                     | 271  | 165   |
| 301200403#335*T1000                     | TES C 335 * 050 □ C 0 @ ^ | C         | 3.3      | 50                | 1.65          | 6           | 1000                  | 332                     | 298  | 133   | 332                     | 298  | 133   |
| 301200404#475*T0200                     | TES D 475 * 050 □ L 0 @ ^ | D         | 4.7      | 50                | 2.35          | 6           | 200                   | 1129                    | 1016 | 452   | 226                     | 203  | 90    |

The parts are supplied in dry pack with Moisture Sensitivity Level (MSL) level 3 - defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

# TAJ CECC Tantalum Capacitors



## SMD Solid Tantalum Chip Capacitors




Capacitors, Fixed, Leadless Surface Mount, Chip, Solid electrolyte Tantalum for use in avionics and industrial applications, tested to CECC Specification 30801-005 and 30801-011 (CTC4).




### CASE DIMENSIONS: millimeters (inches)

| Code | EIA Code | Variant | L±0.20 (0.008) | W+0.20 (0.008)<br>-0.10 (0.004) | H+0.20 (0.008)<br>-0.10 (0.004) | W <sub>1</sub> ±0.20 (0.008) | A+0.30 (0.012)<br>-0.20 (0.008) | S Min.       |
|------|----------|---------|----------------|---------------------------------|---------------------------------|------------------------------|---------------------------------|--------------|
| A    | 3216-18  | 01&11   | 3.20 (0.126)   | 1.60 (0.063)                    | 1.60 (0.063)                    | 1.20 (0.047)                 | 0.80 (0.031)                    | 1.10 (0.043) |
| B    | 3528-21  | 02&12   | 3.50 (0.138)   | 2.80 (0.110)                    | 1.90 (0.075)                    | 2.20 (0.087)                 | 0.80 (0.031)                    | 1.40 (0.055) |
| C    | 6032-28  | 03&13   | 6.00 (0.236)   | 3.20 (0.126)                    | 2.60 (0.102)                    | 2.20 (0.087)                 | 1.30 (0.051)                    | 2.90 (0.114) |
| D    | 7343-31  | 04&14   | 7.30 (0.287)   | 4.30 (0.169)                    | 2.90 (0.114)                    | 2.40 (0.094)                 | 1.30 (0.051)                    | 4.40 (0.173) |

W<sub>1</sub> dimension applies to the termination width for A dimensional area only.



### MARKING A, B, C, D CASE



### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (VOLTAGE CODE) RANGE (LETTER DENOTES CASE SIZE)

#### BS CECC30801-005

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) at 85°C |         |         |         |         |         |         |
|-------------|------|--|---------|---------|---------|---------|---------|---------|
| µF          | Code | 6.3V (J)                                   | 10V (A) | 16V (C) | 20V (D) | 25V (E) | 35V (V) | 50V (T) |
| 0.10        | 104  |  |         |         |         |         | A       | A       |
| 0.15        | 154  |  |         |         |         |         | A       | A/B     |
| 0.22        | 224  |  |         |         |         |         | A       | A/B     |
| 0.33        | 334  |  |         |         |         |         | A       | B       |
| 0.47        | 474  |  |         |         |         | A       | A/B     | C       |
| 0.68        | 684  |  |         |         | A       | A       | A/B     | C       |
| 1.0         | 105  |  |         | A       | A       | A       | B       | C       |
| 1.5         | 155  |  | A       | A       | A       | A/B     | B/C     | D       |
| 2.2         | 225  | A  | A       | A/B     | B       | B       | B/C     | D       |
| 3.3         | 335  | A  | A       | A/B     | B       | B/C     | C/D     | D       |
| 4.7         | 475  | A  | A/B     | B/C     | B/C     | C       | C/D     | D       |
| 6.8         | 685  | A/B  | B       | B/C     | C/D     | C/D     | D       | D       |
| 10          | 106  | A/B  | B/C     | B/C/D   | C       | C/D     | D       |         |
| 15          | 156  | B/C  | B/C/D   | C       | C/D     | D       | D       |         |
| 22          | 226  | B/C/D                                      | C       | C/D     | D       | D       |         |         |
| 33          | 336  | C  | C/D     | D       | D       |         |         |         |
| 47          | 476  | C/D  | D       | D       |         |         |         |         |
| 68          | 686  | C/D  | D       | D       |         |         |         |         |
| 100         | 107  | D  | D       |         |         |         |         |         |

#### BS CECC30801-011 (CTC4)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) at 85°C |         |         |         |         |         |         |
|-------------|------|--|---------|---------|---------|---------|---------|---------|
| µF          | Code | 6.3V (J)                                   | 10V (A) | 16V (C) | 20V (D) | 25V (E) | 35V (V) | 50V (T) |
| 0.10        | 104  |  |         |         |         |         | A       | A       |
| 0.15        | 154  |  |         |         |         |         | A       | B       |
| 0.22        | 224  |  |         |         |         |         | A       | B       |
| 0.33        | 334  |  |         |         |         |         | A       | B       |
| 0.47        | 474  |  |         |         |         | A       | B       | C       |
| 0.68        | 684  |  |         |         | A       |         | B       | C       |
| 1.0         | 105  |  |         | A       |         |         | B       | C       |
| 1.5         | 155  |  | A       |         |         | B       | C       | D       |
| 2.2         | 225  | A  |         |         | B       |         | C       | D       |
| 3.3         | 335  |  |         | B       |         |         | C       | D       |
| 4.7         | 475  |  | B       |         |         | C       | D       | D       |
| 6.8         | 685  | B  |         |         | C       |         | D       |         |
| 10          | 106  |  |         | C       |         | D       | D       |         |
| 15          | 156  |  | C       |         | D       | D       |         |         |
| 22          | 226  | C  |         | D       | D       |         |         |         |
| 33          | 336  |  | D       | D       |         |         |         |         |
| 47          | 476  | D  | D       |         |         |         |         |         |
| 68          | 686  | D  |         |         |         |         |         |         |

NOTE: Voltage ratings are minimum values. AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.



# TAJ CECC Tantalum Capacitors



## SMD Solid Tantalum Chip Capacitors

### HOW TO ORDER

|                |                                     |   |  |   |  |  |
|----------------|-------------------------------------|---|--|---|--|--|
| <b>TAJ</b><br> | <b>A</b><br>                        | <b>475</b><br>  | <b>K</b><br>                             | <b>010</b><br>  | <b>R</b><br>   | <b>FJ</b><br>  |
| <b>Type</b>    | <b>Case Size</b><br>See table above | <b>Capacitance Code</b><br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | <b>Tolerance</b><br>K = ±10%<br>M = ±20% | <b>Rated DC Voltage</b><br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | <b>Termination Finish</b><br>R = 7" T/R 100% Tin<br>S = 13" T/R 100% Tin<br>A = Gold Plating 7" Reel<br>B = Gold Plating 13" Reel<br>H = Tin Lead 7" Reel<br>K = Tin Lead 13" Reel | <b>Suffix</b><br>FJ = CECC 30801-011(CTC4)<br>Y = CECC 30801-005 |



### TECHNICAL SPECIFICATIONS

|                                    |  |     |    |    |    |    |    |    |  |
|------------------------------------|--|-----|----|----|----|----|----|----|--|
| Technical Data:                    | All technical data relate to an ambient temperature of +25°C                                 |     |    |    |    |    |    |    |  |
| Capacitance Range:                 | 0.10 µF to 100 µF  |     |    |    |    |    |    |    |  |
| Capacitance Tolerance:             | ±10%; ±20%   |     |    |    |    |    |    |    |  |
| Rated Voltage DC (V <sub>R</sub> ) | ≤ +85°C:   | 6.3 | 10 | 16 | 20 | 25 | 35 | 50 |  |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C:  | 4   | 7  | 10 | 13 | 17 | 23 | 33 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +85°C:   | 8   | 13 | 20 | 26 | 32 | 46 | 65 |  |
| Surge Voltage (V <sub>S</sub> )    | ≤ +125°C:  | 5   | 8  | 13 | 16 | 20 | 28 | 40 |  |
| Temperature Range:                 | -55°C to +125°C  |     |    |    |    |    |    |    |  |
| Reliability:                       | 1% per 1000 hours at 85°C, V <sub>R</sub> with 0.1Ω/V series Impedance, 60% confidence level |     |    |    |    |    |    |    |  |

# TCH Low ESR Hermetic Series



## SMD Low ESR Conductive Polymer Capacitors in Hermetic package



### FEATURES

- Aerospace & Hi-Rel applications
- Low ESR conductive polymer electrode
- Endurance up to 10 000 hrs. on selected codes
- Ceramic case hermetic packaging
- Stability under humidity and ambient atmosphere exposure
- Large case sizes including CTC-21D provide high capacitance values
- Developed with ESA to suit aerospace applications
- Ongoing ESA qualification
- Manufacturing and screening utilizing AVX patented Q-Process to effectively remove components that may experience excessive parametric shifts or instability in operation life




Elektra Award 2015

### APPLICATIONS

- Aerospace
- Defence
- Power supplies
- Pulse power

### MARKING

#### 9 CASE




For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)


### CASE DIMENSIONS: millimeters (inches)

| Code        | Type             | L                               | W                               | H Max.          | W <sub>1</sub>                  | A                              | S Min.          |
|-------------|------------------|---------------------------------|---------------------------------|-----------------|---------------------------------|--------------------------------|-----------------|
| 9 (CTC-21D) | J-lead (L-shape) | 11.50 ± 0.50<br>(0.453 ± 0.020) | 12.50 ± 0.50<br>(0.492 ± 0.020) | 6.15<br>(0.242) | 12.50 ± 0.50<br>(0.492 ± 0.020) | 1.90 ± 0.50<br>(0.075 ± 0.020) | 7.00<br>(0.276) |
| 9 (CTC-21D) | Undertab         | 11.00 ± 0.20<br>(0.433 ± 0.008) | 12.50 ± 0.20<br>(0.492 ± 0.008) | 5.95<br>(0.234) | 10.50 ± 0.20<br>(0.413 ± 0.008) | 1.50 ± 0.20<br>(0.059 ± 0.008) | 7.80<br>(0.307) |

#### 'J' Lead Termination (L-shape)



#### Undertab Termination



# TCH Low ESR Hermetic Series





## SMD Low ESR Conductive Polymer Capacitors in Hermetic package

### CAPACITANCE AND VOLTAGE RANGE (CASE CODE BEFORE THE BRACKETS)

| Capacitance |      | Rated Voltage DC (V <sub>R</sub> ) at 85°C |       |     |       |       |       |     |        |        |
|-------------|------|--|-------|-----|-------|-------|-------|-----|--------|--------|
| μF          | Code | 10V  | 16V   | 20V | 25V   | 35V   | 50V   | 63V | 75V    | 100V   |
| 15          | 156  |  |       |     |       |       |       |     |        |        |
| 22          | 226  |  |       |     |       |       |       |     |        | 9(150) |
| 33          | 336  |  |       |     |       |       |       |     | 9(120) |        |
| 47          | 476  |  |       |     |       |       | 9(70) |     |        |        |
| 68          | 686  |  |       |     |       |       |       |     |        |        |
| 100         | 107  |  |       |     |       | 9(55) |       |     |        |        |
| 150         | 157  |  |       |     | 9(50) | 9(55) |       |     |        |        |
| 220         | 227  |  | 9(40) |     |       |       |       |     |        |        |
| 330         | 337  | 9(40)                                      |       |     |       |       |       |     |        |        |

Released ratings, (ESR ratings in mOhms in parentheses)

### HOW TO ORDER AVX PART NUMBER

|            |                              |  |                       |  |                                     |             |  |   |   |
|------------|------------------------------|--|-----------------------|--|-------------------------------------|-------------|--|---|---|
| <b>TCH</b> | <b>9</b>                     | <b>687</b>   | <b>M</b>              | <b>016</b>   | <b>W</b>                            | <b>0040</b> | <b>U</b>   |  |  |
| Type       | Case Size<br>See table above | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Tolerance<br>M = ±20% | Rated DC Voltage<br>010 = 10Vdc 050 = 50Vdc<br>016 = 16Vdc 063 = 63Vdc<br>020 = 20Vdc 075 = 75Vdc<br>025 = 25Vdc 100 = 100Vdc<br>035 = 35Vdc | Packaging<br>W = Waffle<br>B = Bulk | ESR in mΩ   | Termination<br>J = 'J' lead L-shape (Gold)<br>L = 'J' lead L-shape (Sn/Pb)<br>U = Undertab | For RoHS compliant products, please select correct termination style.               |   |

### TECHNICAL SPECIFICATIONS

|                                    |   |    |    |    |    |    |    |    |    |     |  |  |
|------------------------------------|---|----|----|----|----|----|----|----|----|-----|--|--|
| Technical Data:                    | All technical data relate to an ambient temperature of +25°C                                |    |    |    |    |    |    |    |    |     |  |  |
| Capacitance Range:                 | 22 μF to 330 μF (for extended range under development, contact manufacturer)                |    |    |    |    |    |    |    |    |     |  |  |
| Capacitance Tolerance:             | ±20%  |    |    |    |    |    |    |    |    |     |  |  |
| Leakage Current DCL:               | 0.1CV   |    |    |    |    |    |    |    |    |     |  |  |
| Rated Voltage (V <sub>R</sub> )    | ≤ +85°C:  | 10 | 16 | 20 | 25 | 35 | 50 | 63 | 75 | 100 |  |  |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C:   | 7  | 11 | 13 | 17 | 23 | 33 | 42 | 50 | 66  |  |  |
| Temperature Range:                 | -55°C to +125°C   |    |    |    |    |    |    |    |    |     |  |  |
| Reliability:                       | 1% per 1000 hours at 85°C, V <sub>r</sub> with 0.1Ω/Vseries impedance, 60% confidence level |    |    |    |    |    |    |    |    |     |  |  |
| Termination Finish:                | Gold Plating (Undertab), Gold Plating (J-lead), Sn/Pb Plating (J-lead)                      |    |    |    |    |    |    |    |    |     |  |  |



# TCH Low ESR Hermetic Series



## SMD Low ESR Conductive Polymer Capacitors in Hermetic package

### RATINGS & PART NUMBER REFERENCE


| AVX Part No.           | Case Size | Capacitance (μF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (μA) | DF Max. (%) | ESR Max. @ 100kHz (mΩ) | 100kHz RMS Current (A) |      |       | MSL |
|------------------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|------------------------|------------------------|------|-------|-----|
|                        |           |                  |                   |                        |                      |                           |               |             |                        | 25°C                   | 85°C | 125°C |     |
| <b>10 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |                        |      |       |     |
| TCH9337M010W0040#      | 9         | 330              | 10                | 85                     | 7                    | 125                       | 330           | 8           | 40                     | 3.16                   | 2.84 | 1.26  | 1   |
| <b>16 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |                        |      |       |     |
| TCH9227M016W0040#      | 9         | 220              | 16                | 85                     | 10                   | 125                       | 352           | 8           | 40                     | 3.16                   | 2.84 | 1.26  | 1   |
| <b>25 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |                        |      |       |     |
| TCH9157M025W0050#      | 9         | 150              | 25                | 85                     | 17                   | 125                       | 375           | 8           | 50                     | 2.83                   | 2.55 | 1.13  | 1   |
| <b>35 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |                        |      |       |     |
| TCH9107M035W0055#      | 9         | 100              | 35                | 85                     | 23                   | 125                       | 350           | 8           | 55                     | 2.69                   | 2.42 | 1.08  | 1   |
| TCH9157M035W0055#      | 9         | 150              | 35                | 85                     | 23                   | 125                       | 525           | 8           | 55                     | 2.69                   | 2.42 | 1.08  | 1   |
| <b>50 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |                        |      |       |     |
| TCH9476M050W0070#      | 9         | 47               | 50                | 85                     | 33                   | 125                       | 235           | 8           | 70                     | 2.39                   | 2.15 | 0.96  | 1   |
| <b>75 Volt @ 85°C</b>  |           |                  |                   |                        |                      |                           |               |             |                        |                        |      |       |     |
| TCH9336M075W0120#      | 9         | 33               | 75                | 85                     | 50                   | 125                       | 248           | 8           | 120                    | 1.82                   | 1.64 | 0.73  | 1   |
| <b>100 Volt @ 85°C</b> |           |                  |                   |                        |                      |                           |               |             |                        |                        |      |       |     |
| TCH9226M100W0150#      | 9         | 22               | 100               | 85                     | 66                   | 125                       | 220           | 8           | 150                    | 1.63                   | 1.47 | 0.65  | 1   |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with a maximum DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

### RECOMMENDED DERATING FACTOR

Voltage and temperature derating as percentage of Vr



# TCH Low ESR Hermetic Series



## SMD Low ESR Conductive Polymer Capacitors in Hermetic package

### QUALIFICATION TABLE

| TEST                              | TCH low ESR hermetic series (Temperature range -55°C to +125°C)   |               |                |                    |                                    |            |            |           |            |            |
|-----------------------------------|---|---------------|----------------|--------------------|------------------------------------|------------|------------|-----------|------------|------------|
|                                   | Condition   |               |                | Characteristics    |                                    |            |            |           |            |            |
| <b>Endurance</b>                  | Apply rated voltage (Ur) at 85°C for 2000 (10000) hours and / or apply category voltage (Uc) at 125°C for 2000 hours through a circuit impedance of <math>3\Omega</math>. Stabilize at room temperature for 2 hours before measuring.   |               |                | Visual examination | no visible damage                  |            |            |           |            |            |
|                                   |   |               |                | DCL                | 1.25 x initial limit               |            |            |           |            |            |
|                                   |   |               |                | $\Delta C/C$       | within $\pm 20\%$ of initial value |            |            |           |            |            |
|                                   |   |               |                | DF                 | 1.5 x initial limit                |            |            |           |            |            |
|                                   |   |               |                | ESR                | 2 x initial limit                  |            |            |           |            |            |
| <b>Storage Life</b>               | Store at 125°C, no voltage applied, for 2000 hours. Stabilize at room temperature for 1-2 hours before measuring.   |               |                | Visual examination | no visible damage                  |            |            |           |            |            |
|                                   |   |               |                | DCL                | 2 x initial limit                  |            |            |           |            |            |
|                                   |   |               |                | $\Delta C/C$       | within $\pm 20\%$ of initial value |            |            |           |            |            |
|                                   |   |               |                | DF                 | 1.5 x initial limit                |            |            |           |            |            |
|                                   |   |               |                | ESR                | 2 x initial limit                  |            |            |           |            |            |
| <b>Humidity</b>                   | Store at 40°C and 90% relative humidity for 56 days, with no applied voltage. Stabilize at room temperature and humidity for min. 2 hours before measuring.   |               |                | Visual examination | no visible damage                  |            |            |           |            |            |
|                                   |   |               |                | DCL                | 1.25 x initial limit               |            |            |           |            |            |
|                                   |   |               |                | $\Delta C/C$       | within $\pm 10\%$ of initial value |            |            |           |            |            |
|                                   |   |               |                | DF                 | initial limit                      |            |            |           |            |            |
|                                   |   |               |                | ESR                | 1.25 x initial limit               |            |            |           |            |            |
| <b>Temperature Stability</b>      | Step  | Temperature°C | Duration (min) |                    | +20°C                              | -55°C      | +20°C      | +85°C     | +125°C     | +20°C      |
|                                   | 1   | +20           | 15             | DCL                | IL*                                | n/a        | IL*        | 10 x IL*  | 12.5 x IL* | IL*        |
|                                   | 2   | -55           | 15             | $\Delta C/C$       | n/a                                | +0/-20%    | $\pm 5\%$  | +20/-0%   | +30/-0%    | $\pm 5\%$  |
|                                   | 3   | +20           | 15             | DF                 | IL*                                | 1.5 x IL*  | IL*        | 1.5 x IL* | 2 x IL*    | IL*        |
|                                   | 4   | +85           | 15             | ESR                | 1.25 x IL*                         | 1.25 x IL* | 1.25 x IL* | 1.5 x IL* | 1.5 x IL*  | 1.25 x IL* |
|                                   | 5   | +125          | 15             |                    |                                    |            |            |           |            |            |
|                                   | 6   | +20           | 15             |                    |                                    |            |            |           |            |            |
| <b>Surge Voltage</b>              | Apply 1.3x rated voltage (Ur) at 85°C through protection series resistance 33 $\Omega$ for Ur $\leq 50V$ or 1.15x rated voltage (Ur) at 85°C through protection series resistance 1000 $\Omega$ for Ur >50V for 1000 cycles of duration 6 min (30 sec charge, 5 min 30 sec discharge) through discharge resistance of 33 $\Omega$ |               |                | Visual examination | no visible damage                  |            |            |           |            |            |
|                                   |   |               |                | DCL                | initial limit                      |            |            |           |            |            |
|                                   |   |               |                | $\Delta C/C$       | within $\pm 20\%$ of initial value |            |            |           |            |            |
|                                   |   |               |                | DF                 | initial limit                      |            |            |           |            |            |
|                                   |   |               |                | ESR                | 1.25 x initial limit               |            |            |           |            |            |
| <b>Mechanical Shock/Vibration</b> | MIL-STD-202, Method 213, Condition C, 100 G peak<br>MIL-STD-202, Method 204, Condition D,<br>10 Hz to 2,000 Hz, 20 G peak   |               |                | Visual examination | no visible damage                  |            |            |           |            |            |
|                                   |   |               |                | DCL                | initial limit                      |            |            |           |            |            |
|                                   |   |               |                | $\Delta C/C$       | within $\pm 10\%$ of initial value |            |            |           |            |            |
|                                   |   |               |                | DF                 | initial limit                      |            |            |           |            |            |
|                                   |   |               |                | ESR                | 1.25 x initial limit               |            |            |           |            |            |

\*Initial Limit

# THH 230°C Hermetic Series



## SMD 230°C High Temperature Tantalum Capacitor in Hermetic Package



### FEATURES

- High temperature applications
- Operational condition 230°C / 0.5U<sub>R</sub> / 1000hrs (2000hrs for selected codes) or 200°C / 0.5U<sub>R</sub> / 10.000hrs
- Ceramic case hermetic packaging
- Large case sizes including CTC-21D provide high capacitance values
- Manufacturing and screening utilizing AVX patented Q-Process to effectively remove components that may experience excessive parametric shifts or instability in operation life




### APPLICATIONS

- Oil drilling
- Extreme temperature applications

For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)

### MARKING



#### 9, I CASE





### CASE DIMENSIONS: millimeters (inches)

| Code        | Type                | L±0.50<br>(0.020)               | W±0.50<br>(0.020)               | H Max.          | W <sub>1</sub> ±0.50<br>(0.020) | A±0.50<br>(0.020)              | S Min.          |
|-------------|---------------------|---------------------------------|---------------------------------|-----------------|---------------------------------|--------------------------------|-----------------|
| 9 (CTC-21D) | J-lead<br>(L-shape) | 11.50<br>(0.453)                | 12.50<br>(0.492)                | 6.15<br>(0.242) | 12.50<br>(0.492)                | 1.90<br>(0.075)                | 7.00<br>(0.276) |
| 9 (CTC-21D) | J-lead<br>(flex)    | 12.10<br>(0.476)                | 12.50<br>(0.492)                | 6.50<br>(0.256) | 12.00<br>(0.472)                | 2.00<br>(0.079)                | 7.20<br>(0.283) |
| 9 (CTC-21D) | Undertab            | 11.00 ± 0.20<br>(0.433 ± 0.008) | 12.50 ± 0.20<br>(0.492 ± 0.008) | 5.95<br>(0.234) | 10.50 ± 0.20<br>(0.413 ± 0.008) | 1.50 ± 0.20<br>(0.059 ± 0.008) | 7.80<br>(0.307) |
| I           | J-lead<br>(L-shape) | 11.50<br>(0.453)                | 6.00<br>(0.236)                 | 2.70<br>(0.106) | 6.00<br>(0.236)                 | 3.50<br>(0.138)                | 4.00<br>(0.157) |
| I           | J-lead<br>(flex)    | 11.90<br>(0.469)                | 6.00<br>(0.236)                 | 3.00<br>(0.118) | 5.50<br>(0.217)                 | 3.60<br>(0.142)                | 4.20<br>(0.165) |
| I           | Undertab            | 11.00 ± 0.20<br>(0.433 ± 0.008) | 6.00 ± 0.20<br>(0.236 ± 0.008)  | 2.50<br>(0.098) | 4.00 ± 0.20<br>(0.157 ± 0.008)  | 3.20 ± 0.20<br>(0.126 ± 0.008) | 4.40<br>(0.173) |


#### 'J' Lead Termination (flex)



#### 'J' Lead Termination (L-shape)



#### Undertab Termination



# THH 230°C Hermetic Series



## SMD 230°C High Temperature Tantalum Capacitor in Hermetic Package

### CAPACITANCE AND VOLTAGE RANGE (CODE DENOTES THE CASE SIZE)

| Capacitance   |      | Rated Voltage DC ( $V_R$ ) at 175°C |         |         |         |         |         |
|---------------|------|-------------------------------------|---------|---------|---------|---------|---------|
| $\mu\text{F}$ | Code | 16V (C)                             | 20V (D) | 25V (E) | 35V (V) | 50V (T) | 63V (J) |
| 4.7           | 475  |                                     |         |         |         |         |         |
| 6.8           | 685  |                                     |         |         |         |         |         |
| 10            | 106  |                                     |         |         |         |         |         |
| 15            | 156  |                                     |         |         |         |         |         |
| 22            | 226  |                                     |         |         |         |         |         |
| 33            | 336  |                                     |         |         |         |         |         |
| 47            | 476  |                                     |         |         |         |         | 9       |
| 68            | 686  |                                     |         |         |         |         |         |
| 100           | 107  |                                     |         |         | 9       |         |         |

Released ratings

Engineering samples - please contact AVX

## HOW TO ORDER

### AVX PART NUMBER

|            |                              |  |                             |  |                                     |                  |  |
|------------|------------------------------|--|-----------------------------|--|-------------------------------------|------------------|--|
| <b>THH</b> | <b>9</b>                     | <b>107</b>   | <b>M</b>                    | <b>035</b>   | <b>W</b>                            | <b>0250</b>      | <b>J</b>   |
| Type       | Case Size<br>See table above | Capacitance Code<br>pF code:<br>1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow) | Tolerance<br>M = $\pm 20\%$ | Rated DC Voltage<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc<br>063 = 63Vdc | Packaging<br>W = Waffle<br>B = Bulk | ESR in $m\Omega$ | Termination<br>J = 'J' lead (L-shape)<br>W = 'J' lead (flex)<br>U = Undertab |



For RoHS compliant products, please select correct termination style.

## TECHNICAL SPECIFICATIONS

|                            |   |    |    |    |    |    |    |  |
|----------------------------|---|----|----|----|----|----|----|--|
| Technical Data:            | All technical data relate to an ambient temperature of +25°C  |    |    |    |    |    |    |  |
| Capacitance Range:         | 6.8 $\mu\text{F}$ to 100 $\mu\text{F}$ (for extended range under development, contact manufacturer) |    |    |    |    |    |    |  |
| Capacitance Tolerance:     | $\pm 20\%$  |    |    |    |    |    |    |  |
| Leakage Current DCL:       | 0.01CV  |    |    |    |    |    |    |  |
| Rated Voltage ( $V_R$ )    | $\leq +85^\circ\text{C}$ :  | 16 | 20 | 25 | 35 | 50 | 63 |  |
| Category Voltage ( $V_C$ ) | $\leq +230^\circ\text{C}$ :   | 8  | 10 | 12 | 17 | 25 | 31 |  |
| Temperature Range:         | -55°C to +230°C   |    |    |    |    |    |    |  |
| Reliability:               | 1% per 1000 hours at 85°C, $V_r$ with 0.1 $\Omega/\text{V}$ series impedance, 60% confidence level  |    |    |    |    |    |    |  |
| Termination Finish:        | Gold Plating (Undertab), Gold Plating (J-lead L shape), Nickel Plating (J-lead flex)                |    |    |    |    |    |    |  |

# THH 230°C Hermetic Series



## SMD 230°C High Temperature Tantalum Capacitor in Hermetic Package

### VOLTAGE VS TEMPERATURE RATING

| AVX Part No.          | Case Size | Capacitance (μF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | DCL Max. (μA) | DF Max. (%) | ESR Max. @ 100kHz (mΩ) | 100kHz RMS Current (A) |      |       | Lifetime at 230°C (hrs) | MSL |
|-----------------------|-----------|------------------|-------------------|------------------------|----------------------|---------------|-------------|------------------------|------------------------|------|-------|-------------------------|-----|
|                       |           |                  |                   |                        |                      |               |             |                        | 25°C                   | 85°C | 230°C |                         |     |
| <b>16 Volt @ 85°C</b> |           |                  |                   |                        |                      |               |             |                        |                        |      |       |                         |     |
| THHI226M016W0500#     | I         | 22               | 16                | 175                    | 8                    | 3.6           | 8           | 500                    | 0.81                   | 0.73 | 0.73  | 2,000                   | 1   |
| THHI476M016W0500#     | I         | 47               | 16                | 175                    | 8                    | 7.5           | 8           | 500                    | 0.81                   | 0.73 | 0.73  | 1,000                   | 1   |
| <b>35 Volt @ 85°C</b> |           |                  |                   |                        |                      |               |             |                        |                        |      |       |                         |     |
| THHI685M035W0500#     | I         | 6.8              | 35                | 175                    | 17                   | 2.4           | 8           | 500                    | 0.81                   | 0.73 | 0.73  | 2,000                   | 1   |
| THHI106M035W0500#     | I         | 10               | 35                | 175                    | 17                   | 3.5           | 8           | 500                    | 0.81                   | 0.73 | 0.73  | 2,000                   | 1   |
| THH9107M035W0250#     | 9         | 100              | 35                | 175                    | 17                   | 35            | 8           | 250                    | 1.26                   | 1.13 | 1.13  | 2,000                   | 1   |
| <b>50 Volt @ 85°C</b> |           |                  |                   |                        |                      |               |             |                        |                        |      |       |                         |     |
| THHI685M050W0500#     | I         | 6.8              | 50                | 175                    | 25                   | 3.4           | 8           | 500                    | 0.81                   | 0.73 | 0.73  | 1,000                   | 1   |
| <b>63 Volt @ 85°C</b> |           |                  |                   |                        |                      |               |             |                        |                        |      |       |                         |     |
| THH9476M063W0250#     | 9         | 47               | 63                | 175                    | 31                   | 29.6          | 8           | 250                    | 1.26                   | 1.13 | 1.13  | 1,000                   | 1   |

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts.


DCL is measured at rated voltage after 5 minutes.

ESR change post 1000hrs allowed up to 3 times catalog limit.

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

### VOLTAGE VS TEMPERATURE RATING

THH 230°C Voltage vs Temperature Rating for 1000 (or 2000) hrs service life



# THH 230°C Hermetic Series



## SMD 230°C High Temperature Tantalum Capacitor in Hermetic Package

### QUALIFICATION TABLE

| TEST                              | THH 230°C hermetic series (Temperature range -55°C to +230°C)  |               |                |                    |                                    |            |            |            |            |            |            |            |            |
|-----------------------------------|--|---------------|----------------|--------------------|------------------------------------|------------|------------|------------|------------|------------|------------|------------|------------|
|                                   | Condition  |               |                | Characteristics    |                                    |            |            |            |            |            |            |            |            |
| <b>Endurance</b>                  | Apply category voltage (Uc) at 230°C for 2000 hours through a circuit impedance of <math><3\Omega/V</math>. Stabilize at room temperature for min. 2 hours before measuring.                             |               |                | Visual examination | no visible damage                  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DCL                | 1.25 x initial limit               |            |            |            |            |            |            |            |            |
|                                   |  |               |                | $\Delta C/C$       | within $\pm 20\%$ of initial value |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DF                 | 1.5 x initial limit                |            |            |            |            |            |            |            |            |
|                                   |  |               |                | ESR                | 3 x initial limit                  |            |            |            |            |            |            |            |            |
| <b>Endurance</b>                  | Apply half rated voltage (0.5xUr) at 200°C for 10000 hours through a circuit impedance of <math><3\Omega/V</math>. Stabilize at room temperature for min. 2 hours before measuring.                      |               |                | Visual examination | no visible damage                  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DCL                | 1.25 x initial limit               |            |            |            |            |            |            |            |            |
|                                   |  |               |                | $\Delta C/C$       | within $\pm 20\%$ of initial value |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DF                 | 1.5 x initial limit                |            |            |            |            |            |            |            |            |
|                                   |  |               |                | ESR                | 3 x initial limit                  |            |            |            |            |            |            |            |            |
| <b>Storage Life</b>               | Store at 230°C, no voltage applied, for 1000 hours. Stabilize at room temperature for min. 2 hours before measuring.   |               |                | Visual examination | no visible damage                  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DCL                | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | $\Delta C/C$       | within $\pm 5\%$ of initial value  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DF                 | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | ESR                | 1.25 x initial limit               |            |            |            |            |            |            |            |            |
| <b>Biased Humidity</b>            | Apply rated voltage (Ur) at 85°C, 85% relative humidity for 1000 hours. Stabilize at room temperature and humidity for min. 2 hours before measuring.  |               |                | Visual examination | no visible damage                  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DCL                | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | $\Delta C/C$       | within $\pm 10\%$ of initial value |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DF                 | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | ESR                | 1.25 x initial limit               |            |            |            |            |            |            |            |            |
| <b>Temperature Stability</b>      | Step   | Temperature°C | Duration (min) |                    | +20°C                              | -55°C      | +20°C      | +85°C      | +125°C     | +175°C     | +200°C     | +230°C     | +20°C      |
|                                   | 1  | +20           | 15             |                    |                                    |            |            |            |            |            |            |            |            |
|                                   | 2  | -55           | 15             | DCL                | IL*                                | n/a        | IL*        | 10 x IL*   | 12.5 x IL* | n/a        | n/a        | n/a        | IL*        |
|                                   | 3  | +20           | 15             |                    |                                    |            |            |            |            |            |            |            |            |
|                                   | 4  | +85           | 15             | $\Delta C/C$       | n/a                                | +0/-20%    | $\pm 5\%$  | +20/-0%    | +30/-0%    | +30/-0%    | +30/-0%    | +30/-0%    | $\pm 5\%$  |
|                                   | 5  | +125          | 15             |                    |                                    |            |            |            |            |            |            |            |            |
|                                   | 6  | +175          | 15             | DF                 | IL*                                | 1.5 x IL*  | IL*        | 1.5 x IL*  | 2 x IL*    | 2 x IL*    | 2 x IL*    | 2 x IL*    | IL*        |
|                                   | 7  | +200          | 15             |                    |                                    |            |            |            |            |            |            |            |            |
|                                   | 8  | +230          | 15             |                    |                                    |            |            |            |            |            |            |            |            |
|                                   | 9  | +20           | 15             | ESR                | 1.25 x IL*                         | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* | 1.25 x IL* |
| <b>Surge Voltage</b>              | Apply 1.3x rated voltage (Ur) at 85°C for 1000 cycles of duration 6 min (30 sec charge, 5 min 30 sec discharge) through a charge / discharge resistance of 33 $\Omega$ .                                 |               |                | Visual examination | no visible damage                  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DCL                | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | $\Delta C/C$       | within $\pm 20\%$ of initial value |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DF                 | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | ESR                | 1.25 x initial limit               |            |            |            |            |            |            |            |            |
| <b>Mechanical Shock/Vibration</b> | MIL-STD-202, Method 213, Condition I, 100 G peak<br>MIL-STD-202, Method 204, Condition D,<br>10 Hz to 2,000 Hz, 20 G peak  |               |                | Visual examination | no visible damage                  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DCL                | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | $\Delta C/C$       | within $\pm 10\%$ of initial value |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DF                 | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | ESR                | 1.25 x initial limit               |            |            |            |            |            |            |            |            |
| <b>Vibration 230°C</b>            | Apply 230°C temperature, no voltage and vibration:<br>10 ~ 2000 ~ 10Hz in 20 min<br>Full amplitude: 3 mm/20g<br>Vibration directions time<br>X, Y Z directions: 4 hours<br>each direction: total 12 hrs. |               |                | Visual examination | no visible damage                  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DCL                | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | $\Delta C/C$       | within $\pm 5\%$ of initial value  |            |            |            |            |            |            |            |            |
|                                   |  |               |                | DF                 | initial limit                      |            |            |            |            |            |            |            |            |
|                                   |  |               |                | ESR                | 1.25 x initial limit               |            |            |            |            |            |            |            |            |

\*Initial Limit

# High Reliability Tantalum MSL



## Storage, Bake out, and Handling Recommendations


AVX Biddeford ships all COTS+, military, space level, and \*medical grade surface mount tantalum capacitors in moisture resistant bags as a part of best practice. This includes CWR, TAZ, TBJ, TBC, T4C, T4J, TBM, and TCP product. This has improved our service to customers by alleviating the potential for long term exposure to high humidity conditions during shipping and storage.

Biddeford product that is considered to be MSL 3 includes TBMs, TCPs, TCBs, TCSs, T4Cs, T4Js, TBJ V, U and E case, and TAZ (CWR09/19/29) H, V and X case. The remainder of our tantalum capacitors are rated MSL 1 for moisture (per J-STD-020D). AVX MSL 1 Tantalum capacitors are unaffected by storage for 2 years at the following conditions: a temperature between -10°C and +35°C, maximum of 85% RH, and atmospheric pressure between 860 mbar and 1060mbar. Exposure to humidity in excess of the above conditions can

occur during shipping or storage; this may affect the leakage current of resin protected capacitors and possibly result in damaging the capacitors during reflow.

If high exposure occurs, MSL 1 product can be dried by baking at temperatures between 85°C for 16 hours to 125°C for 4 hours. Product packaged in tape and reel requires special handling as the tape and reels cannot withstand these temperatures. Extended bake out at 55°C with less than 10% humidity for 48-hours can be performed for product in tape and reel packaging. MSL 3 product should be baked out for 168 hours at 40°C.

The reflow profile below is recommended to ensure parametric integrity of the capacitors is maintained. An improper combination of temperature and time can lead to damage in the dielectric of the component and this profile minimizes that risk.



\*For implantable medical applications please contact the factory for further recommendations.

# TAZ Cots+, CWR09, CWR19, CWR29, TAZ HRC5000 and TAZ HRC6000 Series



## Tape & Reel Packaging

Solid Tantalum Chip TAZ Tape and reel packaging for automatic component placement.

Please enter required Suffix on order. Bulk packaging is standard.

### TAZ TAPING SUFFIX TABLE

| Case Size reference | Tape width mm | P mm | 180mm (7") reel |      | 330mm (13") reel |      |
|---------------------|---------------|------|-----------------|------|------------------|------|
|                     |               |      | Suffix          | Qty. | Suffix           | Qty. |
| A                   | 8             | 4    | R               | 2500 | S                | 9000 |
| R                   | 8             | 4    | R               | 2500 | S                | -    |
| B                   | 12            | 4    | R               | 2500 | S                | 9000 |
| C                   | 12            | 4    | R               | 2500 | S                | 9000 |
| D                   | 12            | 4    | R               | 2500 | S                | 8000 |
| E                   | 12            | 4    | R               | 2500 | S                | 8000 |
| F                   | 12            | 8    | R               | 1000 | S                | 3000 |
| G                   | 12            | 8    | R               | 500  | S                | 2500 |
| H                   | 12            | 8    | R               | 500  | S                | 2500 |
| X                   | 12            | 8    | R               | 500  | S                | 2000 |

| Total Tape Thickness – K max |                          |
|------------------------------|--------------------------|
| TAZ                          |                          |
| Case size reference          | Millimeters (Inches) DIM |
| A                            | 2.0 (0.079)              |
| R                            | 2.0 (0.079)              |
| B                            | 4.0 (0.157)              |
| D                            | 4.0 (0.157)              |
| E                            | 4.0 (0.157)              |
| F                            | 4.0 (0.157)              |
| G                            | 4.0 (0.157)              |
| H                            | 4.0 (0.157)              |
| X                            | 4.0 (0.157)              |

| Code           | 8mm Tape             |                                    | 12mm Tape            |                                    |
|----------------|----------------------|------------------------------------|----------------------|------------------------------------|
| P*             | 4±0.1<br>or<br>8±0.1 | (0.157±0.004)<br><br>(0.315±0.004) | 4±0.1<br>or<br>8±0.1 | (0.157±0.004)<br><br>(0.315±0.004) |
| G              | 0.75 min             | (0.03 min)                         | 0.75 min             | (0.03 min)                         |
| F              | 3.5±0.04             | (0.138±0.002)                      | 5.5±0.05             | (0.22±0.002)                       |
| E              | 1.75±0.1             | (0.069±0.004)                      | 1.75±0.1             | (0.069±0.004)                      |
| W              | 8±0.3                | (0.315±0.012)                      | 12±0.3               | (0.472±0.012)                      |
| P <sub>2</sub> | 2±0.05               | (0.079±0.002)                      | 2±0.05               | (0.079±0.002)                      |
| P <sub>0</sub> | 4±0.1                | (0.157±0.004)                      | 4±0.1                | (0.157±0.004)                      |
| D              | 1.5±0.1<br>-0        | (0.059±0.004)<br>(-0)              | 1.5±0.1<br>-0        | (0.059±0.004)<br>(-0)              |
| D <sub>1</sub> | 1.0 min              | (0.039 min)                        | 1.5 min              | (0.059 min)                        |


\*See taping suffix tables for actual P dimension (component pitch).

### TAPE SPECIFICATION

Tape dimensions comply to EIA RS 481 A  
Dimensions A<sub>0</sub> and B<sub>0</sub> of the pocket and the tape thickness, K, are dependent on the component size.

Tape materials do not affect component solderability during storage.

Carrier Tape Thickness <0.4mm





# TAJ ESCC, TAJ CECC, TBJ CWR11, TBJ COTS+, T4J, TBM, TCB, TCS, TES, TBC CWR15, TBC COTS+, TBC HRC5000, TBC HRC6000 and T4C Series

## Tape & Reel Packaging



Tape and reel packaging for automatic component placement. Please enter required Suffix on order. Bulk packaging is not available.

### TAPE SPECIFICATION

Tape dimensions comply to EIA 481-1 Dimensions A<sub>0</sub> and B<sub>0</sub> of the pocket and the tape thickness, K, are dependent on the component size. Tape materials do not affect component solderability during storage. Carrier Tape Thickness <0.4mm.

### TAPING TABLE TAJ ESCC, TAJ CECC, TBJ CWR11, TBJ COTS+, T4J, TBM, TES, TCB AND TCS SERIES

| Case Size | Tape width mm | P mm | 180mm (7") reel Qty. | 330mm (13") reel Qty. |
|-----------|---------------|------|----------------------|-----------------------|
| A         | 8             | 4    | 2,000                | 8,000                 |
| B         | 8             | 4    | 2,000                | 8,000                 |
| C         | 12            | 8    | 500                  | 3,000                 |
| D         | 12            | 8    | 500                  | 2,500                 |
| E         | 12            | 8    | 400                  | 1,500                 |
| U         | 16            | 8    | 400                  | -                     |
| V         | 12            | 8    | 400                  | 1,500                 |

### TAPING SUFFIX TABLE TBC CWR15, COTS+, TBC HRC5000, TBC HRC6000 AND T4C SERIES

| Case Size | Tape width mm | P mm | 100mm (4") reel |       | 180mm (7") reel |        |
|-----------|---------------|------|-----------------|-------|-----------------|--------|
|           |               |      | Designator      | Qty.  | Designator      | Qty.   |
| A         | 12            | 4    |                 |       | R               | 2,000  |
| B         | 12            | 8    |                 |       | R               | 1,000  |
| K         | 8             | 2    | Q               | 1,000 | P               | 10,000 |
| L         | 8             | 4    | X               | 500   | R               | 3,500  |
| R         | 8             | 4    | X               | 500   | R               | 2,500  |
| S         | 12            | 4    |                 |       | R               | 2,000  |


### PLASTIC TAPE DIMENSIONS TAJ ESCC, TAJ CECC, TBJ CWR11, TBJ COTS+, T4J, TBM, TES, TCB AND TCS SERIES

| Case | A0±0.10 | B0±0.10 | K±0.10 | W±0.30 | E±0.10 | F±0.05 | G min. | P±0.10 | P2±0.05 | P0±0.10 | D <sup>+0.20</sup> <sub>-0.00</sub> | D1 <sup>+0.25</sup> <sub>-0.00</sub> |
|------|---------|---------|--------|--------|--------|--------|--------|--------|---------|---------|-------------------------------------|--------------------------------------|
| A    | 1.83    | 3.57    | 1.87   | 8.00   | 1.75   | 3.50   | 0.75   | 4.00   | 2.00    | 4.00    | 1.50                                | 1.00                                 |
| B    | 3.15    | 3.77    | 2.22   | 8.00   | 1.75   | 3.50   | 0.75   | 4.00   | 2.00    | 4.00    | 1.50                                | 1.00                                 |
| C    | 3.45    | 6.40    | 2.92   | 12.00  | 1.75   | 5.50   | 0.75   | 8.00   | 2.00    | 4.00    | 1.50                                | 1.50                                 |
| D    | 4.48    | 7.62    | 3.22   | 12.00  | 1.75   | 5.50   | 0.75   | 8.00   | 2.00    | 4.00    | 1.50                                | 1.50                                 |
| E    | 4.50    | 7.50    | 4.50   | 12.00  | 1.75   | 5.50   | 0.75   | 8.00   | 2.00    | 4.00    | 1.50                                | 1.50                                 |
| U    | 6.19    | 7.66    | 4.72   | 16.00  | 1.75   | 7.50   | 0.75   | 8.00   | 2.00    | 4.00    | 1.50                                | 1.50                                 |
| V    | 6.43    | 7.44    | 3.84   | 12.00  | 1.75   | 5.50   | 0.75   | 8.00   | 2.00    | 4.00    | 1.50                                | 1.50                                 |


### PLASTIC TAPE DIMENSIONS TBC CWR15, COTS+, TBC HRC5000, TBC HRC6000 AND T4C SERIES

| Case | A0±0.10 | B0±0.10 | K±0.10 | W±0.30 | E±0.10 | F±0.05 | G min. | P±0.10 | P2±0.05 | P0±0.10 | D±0.05 |
|------|---------|---------|--------|--------|--------|--------|--------|--------|---------|---------|--------|
| A    | 1.91    | 3.53    | 1.93   | 12.00  | 1.75   | 5.50   | 0.75   | 4.00   | 2.00    | 4.00    | 1.55   |
| B    | 3.30    | 4.17    | 2.03   | 12.00  | 1.75   | 5.50   | 0.75   | 8.00   | 2.00    | 4.00    | 1.55   |
| K    | 0.75    | 1.26    | 0.67   | 8.00   | 1.75   | 3.50   | 0.75   | 2.00   | 2.00    | 4.00    | 1.55   |
| L    | 1.05    | 1.90    | 1.17   | 8.00   | 1.75   | 3.50   | 0.75   | 4.00   | 2.00    | 4.00    | 1.55   |
| R    | 1.65    | 2.45    | 1.68   | 8.00   | 1.75   | 3.50   | 0.75   | 4.00   | 2.00    | 4.00    | 1.55   |
| S    | 1.91    | 3.53    | 1.93   | 12.00  | 1.75   | 5.50   | 0.75   | 4.00   | 2.00    | 4.00    | 1.55   |

### REEL DIMENSIONS



| Reel Size     | Tape | A        | B      | C         | W           | t         |
|---------------|------|----------|--------|-----------|-------------|-----------|
| 180mm (7")    | 12mm | 178±2.00 | 50 min | 13.0±0.50 | 12.4+1.5/-0 | 1.50±0.50 |
| 180mm (7")    | 8mm  | 178±2.00 | 50 min | 13.0±0.50 | 8.4+1.5/-0  | 1.50±0.50 |
| 330mm (13")   | 12mm | 328±2.00 | 50 min | 13.0±0.50 | 12.4+1.5/-0 | 1.50±0.50 |
| 330mm (13")   | 8mm  | 328±2.00 | 50 min | 13.0±0.50 | 8.4+1.5/-0  | 1.50±0.50 |
| 108mm (4.25") | 8mm  | 108±2.00 |        | 13.0±0.50 | 8.4+1.5/-0  | 1.50±0.50 |



### COVER TAPE NOMINAL DIMENSIONS

Thickness: 75µm  
 Width of tape: 5.5mm (8mm tape)  
 9.5mm (12mm tape)


# TCH and THH

## Packaging



### TCH AND THH PACKAGING SPECIFICATION



The dimensions of the tray see in the figure below. Tolerance of dimensions are  $\pm 0.1$  mm. Both case size "G" and "I" have 40 pcs per tray.



### OVERALL CHIP TRAY SIZE

| Size                 | Height   | Flatness |
|----------------------|--|----------|
| 50.80mm $\pm$ 0.10mm | 3.96mm <sup>+0.05mm</sup> / <sub>-0.08mm</sub> | 0.10mm   |

### PLASTIC CHIP TRAY



E Case

# Tantalum Wet Electrolytic Capacitor



## Technical Summary and Application Guidelines

### INTRODUCTION

The structure of a Tantalum Wet Electrolytic Capacitor consists of four main elements: a primary electrode (anode), dielectric, a secondary electrode system (cathode) and a wet (liquid) electrolyte. The first, positive electrode (the anode) is a very high surface area structure made of pure tantalum metal. As with anodes prepared for surface mount devices, they are made by pressing and sintering pure tantalum powder together with an embedded tantalum wire (for later electrical contact) into, in this case, a cylindrical pellet of extremely high internal surface area capable of achieving high Capacitance at a given rated voltage. Next, the dielectric, a highly resistive insulating layer, is formed. The dielectric material is a thin film of tantalum pentoxide ( $Ta_2O_5$ ) created by electrolytic oxidation of the anode surface, a process which grows the film over all of the internal surface area of the anode. The second electrode (cathode) is an extremely high surface area material actually applied to the inside surface of the pure tantalum can that provides the external housing for the device. The cathode system in wet capacitors provides good mechanical robustness and excellent contact with the liquid electrolyte, which is the functional connection between anode and cathode. All are contained within the can which is hermetically sealed, with an external anode lead connected to the embedded anode wire, and an external cathode lead connected to the can.




Figure 1 a. Basic Tantalum Wet Electrolytic Capacitor System




Figure 1 b. Typical Formed anode pellet structure

### Wet

tantalum capacitors have been utilized for many years in high energy storage applications where volumetric efficiency and high reliability are essential requirements. The first wet tantalum capacitors were developed in the middle of 20th century and comprised a tantalum anode surrounded by an electrolyte inside a silver case with an epoxy end seal.

This design was problematic in that it could be prone to leakage of the electrolyte through the epoxy seal. It also had a limited ability to withstand any reverse voltage. The silver case material was later replaced by pure tantalum, which provided more stable performance characteristics over a wide range of applications.

The use of a tantalum case made it easier to construct a tantalum glass-to-metal end-seal that could be laser-welded to the tantalum can, thus making a fully hermetic capacitor. This construction addressed the risk of fluid leakage from the part and improved overall reliability.

The original design also included the use of a porous, high surface area tantalum sleeve inside the case which acted as the cathode system. The design with tantalum sleeve was adopted by MIL-PRF-39006 and remains the qualified standard tantalum wet capacitors (**AVX TWC series family**).




Figure 2. Typical Wet Tantalum Capacitor Construction

Because the bulk of the capacitance attainable is strongly dependent on the area of the cathode, alternative cathode systems, directly coated onto the interior of the tantalum can, were developed, such as used by **AVX TWA series family**. This system not only increases the overall area of the cathode, but also increases the internal volume available for the anode, thus significantly increasing the potential capacitance/voltage ratings available in each case size. The disadvantage of the alternative cathode system is a limited reverse voltage capability.

The key benefits of wet tantalum electrolyte systems are:

- Large case sizes capable of offering high Capacitance values at high operating voltages.
- Wide operational temperature ranges -55 to 125°C, with special designs up to 230°C
- Wide working voltage range up to 125V
- High volumetric efficiency.

Disadvantages compared to solid tantalum series are:

- Lower electrolyte conductivity resulting in higher ESR.
- Reduced capacitance and increased ESR at low temperatures.
- Risk of hydrogen generation.
- Higher material and manufacturing cost.

Compared to solid tantalum technologies e.g. ( $MnO_2$  or polymer electrolyte), wet tantalum capacitors exhibit a higher surge current capability with a higher breakdown voltage (BDV) close to their dielectric formation voltage. This results in capacitors that require less voltage derating.

Their lower electrolyte conductivity results in a greater capacitance drop with frequency, suiting wet tantalum electrolytic capacitors ideally to high reliability bulk capacitance applications.

### SECTION 1 ELECTRICAL CHARACTERISTICS AND EXPLANATION OF TERMS

#### 1.1 CAPACITANCE

##### 1.1.1 Rated Capacitance

Capacitance is measured at 120Hz and 25°C with 2.0V DC bias applied. A small reduction in capacitance level (<2%) may be observed at rated voltage.

##### 1.1.2 Capacitance Tolerance

This is the permissible variation of the actual value of the capacitance from the rated value. For additional reading, please consult the AVX technical publication “Capacitance Tolerances for Solid Tantalum Capacitors”.

##### 1.1.3 Temperature dependence of capacitance.

The capacitance of a tantalum capacitor varies with temperature. This variation itself is dependent to a small extent on the case size and rating as shown in Figure 1.1.3; capacitance limits for individual ratings at -55°C, +85°C and +125°C are given in the data sheet.

##### 1.1.4 Frequency dependence of capacitance.

Capacitance levels decrease with increasing frequency. Figure 1.1.4a across shows the typical capacitance versus frequency behavior of a TWC series (conventional tantalum sleeve) design. Figure 1.1.4b illustrates typical capacitance characteristics versus frequency for several different ratings of the TWA series (wet system with alternative cathode).

Typical Range of Capacitance Change over Temperature




Figure 1.1.3: Typical Capacitance Change Limits vs. Temperature




Figure 1.1.4 a: TWC Typical Capacitance vs. Frequency




Figure 1.1.4 b: TWA Typical Capacitance vs. Frequency

### 1.2 VOLTAGE

#### 1.2.1 Rated DC Voltage ( $V_R$ )

This is the maximum continuous DC voltage that the part may be subjected to at temperatures from  $-55^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ .

#### 1.2.2 Category voltage ( $V_C$ ).

This is the maximum voltage that may be applied continuously to a capacitor over its temperature range. It is equal to the rated voltage  $V_R$  from  $-55^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ , beyond which it is subject to a linear derating, to 2/3

$V_R$  at  $125^{\circ}\text{C}$  See Figure 1.2.1 below for voltage derating with temperature.




Figure 1.2.1 Voltage Derating over Temperature

The maximum working voltage for temperatures between  $85^{\circ}\text{C}$  and  $125^{\circ}\text{C}$  can also be found from the following formula:

$$V_{\max} = \left(1 - \frac{(T - 85)}{125}\right) \times V_R$$

where T is the required operating temperature.

#### 1.2.3 Surge voltage ( $V_S$ ).

This is the highest voltage that may be applied to a capacitor for short periods of time in circuits with minimum series resistance of 33Ohms. This includes the peak AC ripple voltage in addition to the DC bias voltage.

Table 1.2.3 below illustrates the maximum allowable surge voltage for each voltage rating.

| Voltage   |   |
|---|---|
| Rated ( $85^{\circ}\text{C}$ ) ( $85^{\circ}\text{C}$ ) | Surge ( $85^{\circ}\text{C}$ ) ( $85^{\circ}\text{C}$ ) |
| 6   | 6.9   |
| 8   | 9.2   |
| 10  | 11.5  |
| 15  | 17.3  |
| 25  | 28.8  |
| 30  | 34.5  |
| 50  | 57.5  |
| 60  | 69.0  |
| 75  | 86.3  |
| 100   | 115.0   |
| 125   | 144.0   |

Table 1.2.3

$85^{\circ}\text{C}$  Surge Voltage ratings

#### TWC Series Family Surge Test:

Typical surge voltage testing consists of 1000 cycles of an applied 30 second surge voltage followed by a 5.5 minute discharge period. Voltage application is made through a resistance of  $(1,000 \pm 100)$  ohms in series with the capacitor. Each surge voltage cycle is performed in such a manner that the capacitor is discharged through a 1 kOhm resistor at the end of 30 seconds of applied voltage. Upon completing the test, the capacitors are allowed to stabilize at room temperature and measured to the following limits:

1. Capacitance shall be within the initial  $25^{\circ}\text{C}$  tolerance
2. DC leakage shall not exceed the initial  $25^{\circ}\text{C}$  limit
3. DF shall not exceed the initial  $25^{\circ}\text{C}$  limit
4. Capacitors shall be visually examined for mechanical damage and leakage of electrolyte.

#### TWA Series Family Surge Test:

The surge voltage may be applied up to 10 times in an hour for periods of up to 30 seconds at a time. The surge voltage must not be used as the design parameter for circuits in which, in the normal course of operation, the capacitor is periodically charged and discharged to.

#### 1.2.4 High Temperature Voltage ( $V_T$ )

High temperature capacitor series (TWA-Y and TWC-Y) (designed for operation above  $125^{\circ}\text{C}$ ) can be operated at 60% of their rated DC voltage ( $V_R$ ) at  $200^{\circ}\text{C}$  for a period specified in their individual data sheets. The specialty high temperature TWA-X series is designed to service at extremes  $200-230^{\circ}\text{C}$ . For maximum operating voltage and time at the temperature see the TWA-X series specification.

#### 1.2.5 Reverse voltage and Non-Polar operation.

Tantalum wet capacitors are inherently polar devices with the positive terminal identified on the body of the component. It is advisable to avoid the application of reverse voltage at all times. However, they do have the capability to withstand some reverse voltage as follows:

#### TWC Series Family Reverse Voltage Operation

TWC series allow limited reverse voltage levels of up to 3V for a maximum of 125 Hours. Capacitors evaluated to these conditions have met the following requirements:

1. DCL shall not exceed 125% of the initial value specified.
2. Capacitance shall remain within the initial tolerance (5%, 10%, 20%).
3. DF shall not exceed the initial limit specified.

#### TWA Series Family Reverse Voltage Operation

Continuous application of reverse voltage without normal polarization may result in an increase in leakage current. Reverse voltage ratings are designed to cover exceptional conditions where small level excursions into incorrect polarity may occur. The values quoted do not apply to continuous reverse operation.

Any peak reverse voltage applied to the capacitor must meet the following criteria:

- The peak reverse voltage must be less than or equal to 1.5 volts and the product of the peak current times the duration of the reverse transient must be less than or equal to 0.05 ampere-second.
- The repetition rate of the reverse voltage surges must be less than 10 Hz.

### Non-Polar Operation

Under conditions where the continuous application of a reverse voltage could occur, two similar capacitors should be used in a back-to-back configuration with the negative terminations having a common connection. This combination will give a total capacitance of approximately one half of the nominal capacitance of each capacitor. Under conditions of isolated pulses or during the first few cycles, the capacitance may approach the full nominal value.

### 1.2.6 Superimposed A.C. Voltage (Vrms) - Ripple Voltage.

This is the maximum rms alternating voltage, superimposed on a DC voltage, that may be applied to a capacitor.

The sum of the DC voltage and peak value of the superimposed ac voltage must not exceed the category voltage,  $V_C$ .

## 1.3 IMPEDANCE, (Z) AND EQUIVALENT SERIES RESISTANCE (ESR)

### 1.3.1 Impedance, Z.

This is the ratio of voltage to current at a specified frequency. The impedance is measured at -55°C and 120Hz.

### 1.3.2 Equivalent Series Resistance, ESR.


The ESR of a wet tantalum behaves much the same as a solid tantalum capacitor. It will decrease as frequency increases and generally resonance is achieved above 100 kHz. ESR is measured at 120Hz and 25°C with 2.0V DC bias applied. The ESR is frequency dependent and can be found by using the relationship:

$$ESR = \tan \delta / 2\pi fC$$


Where f is the frequency in Hz, and C is the capacitance in farads. ESR is one of the contributing factors to impedance, and at high frequencies (10kHz and above) it becomes the dominant factor.

### 1.3.3 Frequency dependence of ESR.

ESR and Impedance both reduce with increasing frequency. At lower frequencies the values diverge as the extra contributions to impedance (due to the reactance of the capacitor) become more significant. In the range (1–10) kHz the values of impedance and ESR are almost identical, while at higher frequencies (and beyond the resonant point of the capacitor) impedance again increases due to the inductance of the capacitor.



Graph 1.3.3.a TWC Frequency Dependence of ESR



Graph 1.3.3. b TWA Frequency Dependence of ESR

### 1.3.5 Temperature dependence of Impedance, Z and ESR.

ESR and impedance vary with temperature, with the most significant changes occurring at low temperature. ESR and Impedance can increase by a factor of 20 to 30 times at the lower limit of -55°C; low temperature impedance limits for each rating are given in the individual data sheets.

At High temperatures ESR levels reduce slightly. ESR is typically halved at +85°C and is reduced to almost a third at +125°C.

### 1.4 D.C. LEAKAGE CURRENT

#### 1.4.1 Leakage current, DCL.

The leakage current is dependent on the voltage applied, the time over which the voltage is applied and the component temperature. It is measured at +25°C with rated voltage applied. A protective resistance of 1000Ω is connected in series with the capacitor in the measuring circuit. Three to five minutes after application of the rated voltage the leakage current must not exceed the maximum values indicated in the individual data sheet.

Leakage limits are specified for 25°C and 85°C with rated voltage applied, and for 125°C with category (2/3 rated) voltage applied.

Wet tantalum technology is characterized by extremely low leakage current, typically less than 0.0002CV (about 50 times lower than solid tantalum technology).

#### 1.4.2 Temperature Dependence of Leakage current.

Leakage current increases with increasing temperature. In general, there will be a 10 to 12 times increase at 85°C and 125°C respectively. DCL limits for individual ratings at -55°C, +85°C and +125°C are given in the data sheet.

#### 1.4.3 Voltage dependence of the leakage current.

When operated at applied voltages less than the rated voltage, leakage current will be greatly reduced.

When operated at applied voltages less than the rated voltage, reliability in any given application will be increased.

### 1.5 A.C. OPERATION, POWER DISSIPATION AND RIPPLE CURRENT

#### 1.5.1 A.C. Operation.

In an A.C. application heat is generated within the capacitor primarily by the a.c. component of the signal (which will depend upon the signal form, amplitude and frequency), and secondarily by the DC leakage (for most practical purposes this, second factor is insignificant). The actual power dissipated in the capacitor can be calculated using the formula:

$$P = I^2R$$

rearranged to:

$$I = \text{SQRT}(P/R) \dots (\text{Eq. 1})$$

Where: I = rms ripple current, amperes  
 R = equivalent series resistance, ohms  
 U = rms ripple voltage, volts  
 P = power dissipated, watts  
 Z = impedance, ohms, at the frequency under consideration.

The maximum a.c. ripple voltage (U<sub>max</sub>) is calculated from Ohms' law:

$$U_{\text{max}} = IR \dots (\text{Eq. 2})$$

Where P is the maximum specified permissible power dissipation.

However care must be taken to ensure that:

1. The DC working voltage of the capacitor must not be exceeded by the sum of the positive peak of the applied a.c. voltage and the DC bias voltage.
2. The sum of the applied DC bias voltage and the negative a.c. voltage peak must not exceed the reverse voltage specification limit.

#### 1.5.2 Power Dissipation

Power dissipation is a measure of the power required to heat the capacitor to a certain temperature above ambient. Power dissipation is a function of case size and This is used in the above equations to calculate ripple current limits.

#### 1.5.3 Ripple Current.

Ripple current is referenced at 40kHz at 2/3 rated voltage at 85°C and multipliers for applied voltages of different percentages of rated voltage, and for different frequencies, have been calculated over the temperature range from -55°C to 125°C. These are shown in table 1.5.3.

The reference point (40kHz at 2/3 rated voltage at 85°C) is highlighted in yellow in the table.

| Frequency of applied ripple current | 120 Hz |     |      |      | 800 Hz |      |      |      | 1 kHz |      |      |      |   |
|-------------------------------------|--------|-----|------|------|--------|------|------|------|-------|------|------|------|---|
|                                     | ≤ 55   | 85  | 105  | 125  | ≤ 55   | 85   | 105  | 125  | ≤ 55  | 85   | 105  | 125  |   |
| Ambient still air temperature (°C)  |        |     |      |      |        |      |      |      |       |      |      |      |   |
| % of 85°C rated peak voltage        | 100%   | 0.6 | 0.39 | –    | –      | 0.71 | 0.43 | –    | –     | 0.72 | 0.45 | –    | – |
|                                     | 90%    | 0.6 | 0.46 | –    | –      | 0.71 | 0.55 | –    | –     | 0.72 | 0.55 | –    | – |
|                                     | 80%    | 0.6 | 0.52 | 0.35 | –      | 0.71 | 0.62 | 0.42 | –     | 0.72 | 0.62 | 0.42 | – |
|                                     | 70%    | 0.6 | 0.58 | 0.44 | –      | 0.71 | 0.69 | 0.52 | –     | 0.72 | 0.7  | 0.52 | – |
| 66-2/3%                             | 0.6    | 0.6 | 0.46 | 0.27 | 0.71   | 0.71 | 0.55 | 0.32 | 0.72  | 0.72 | 0.55 | 0.32 |   |

| Frequency of applied ripple current | 10 kHz |      |      |      | 40 kHz |    |      |      | 100 kHz |     |      |      |   |
|-------------------------------------|--------|------|------|------|--------|----|------|------|---------|-----|------|------|---|
|                                     | ≤ 55   | 85   | 105  | 125  | ≤ 55   | 85 | 105  | 125  | ≤ 55    | 85  | 105  | 125  |   |
| Ambient still air temperature (°C)  |        |      |      |      |        |    |      |      |         |     |      |      |   |
| % of 85°C rated peak voltage        | 100%   | 0.88 | 0.55 | –    | –      | 1  | 0.63 | –    | –       | 1.1 | 0.69 | –    | – |
|                                     | 90%    | 0.88 | 0.67 | –    | –      | 1  | 0.77 | –    | –       | 1.1 | 0.85 | –    | – |
|                                     | 80%    | 0.88 | 0.76 | 0.52 | –      | 1  | 0.87 | 0.59 | –       | 1.1 | 0.96 | 0.65 | – |
|                                     | 70%    | 0.88 | 0.85 | 0.64 | –      | 1  | 0.97 | 0.73 | –       | 1.1 | 1.07 | 0.8  | – |
| 66-2/3%                             | 0.88   | 0.88 | 0.68 | 0.4  | 1      | 1  | 0.77 | 0.45 | 1.1     | 1.1 | 0.85 | 0.5  |   |

Fig. 1.5.3 Ripple current multipliers vs. Frequency, temperature and applied voltage

### 1.6 SOLDERING CONDITIONS AND BOARD ATTACHMENT


#### 1.6.1 Wave Soldering.

AVX leaded tantalum capacitors are designed for printed circuit board (pcb) attachment via a wave soldering operation. The soldering temperature and time should be the minimum required for a good connection. After insertion into the pcb, the exposed leads can be passed through wave solder, a suitable temperature/time combination being 230°C – 250°C for 3-5 seconds. Figure 1.7.1 illustrates the allowable range of peak temperature versus time for wave soldering.

# Tantalum Wet Electrolytic Capacitor




## Technical Summary and Application Guidelines



Graph 1.6.1. Allowable range of peak temp./time combinations for wave soldering

As small parametric shifts may be noted immediately after wave solder, components should be allowed to stabilize at room temperature prior to electrical testing. After soldering, the assembly should be allowed to cool naturally. In the event that assisted cooling is used, the rate of change in temperature should not exceed that used in reflow. A recommended wave solder profile is shown below:



Graph 1.6.2. Recommended Wave Solder Profile

## 1.7 RELIABILITY CALCULATION

The predicted reliability of a wet tantalum capacitor in an application can be calculated using the equation defined in MIL-HDBK-217 as seen below:

$$\lambda_P = \lambda_b \times \pi_T \times \pi_C \times \pi_V \times \pi_{SR} \times \pi_Q \times \pi_E$$

Failures/10<sup>6</sup> Hours

where:

$\lambda_P$  = part failure rate

$\lambda_b$  = base failure rate

$\pi$  = factors that modify the base failure rate

For wet tantalum capacitors the base failure rate ( $\lambda_b$ ) is:

$$\lambda_b = 0.0004$$

The  $\pi$  factors should be determined from the tables that follow which outline the values for each variable as they pertain to individual components and the applications in which they are utilized.

| Temperature Factor $\pi_T$ |         | Capacitance Factor $\pi_C$ |           | Voltage Stress Factor $\pi_V$ |         | Quality Factor $\pi_Q$ |         |
|----------------------------|---------|----------------------------|-----------|-------------------------------|---------|------------------------|---------|
| T (°C)                     | $\pi_T$ | Cap (μF)                   | * $\pi_C$ | Voltage Stress                | $\pi_V$ | Quality                | $\pi_Q$ |
| 20                         | 0.91    | 1                          | 1.00      | 0.1                           | 1       | D                      | 0.001   |
| 30                         | 1.1     | 4                          | 1.38      | 0.2                           | 1       | C                      | 0.01    |
| 40                         | 1.3     | 10                         | 1.70      | 0.3                           | 1       | S, B                   | 0.03    |
| 50                         | 1.6     | 15                         | 1.86      | 0.4                           | 1       | R                      | 0.1     |
| 60                         | 1.8     | 33                         | 2.23      | 0.5                           | 1       | P                      | 0.3     |
| 70                         | 2.2     | 68                         | 2.64      | 0.6                           | 2       | M                      | 1       |
| 80                         | 2.5     | 100                        | 2.88      | 0.7                           | 15      | L                      | 1.5     |
| 90                         | 2.8     | 220                        | 3.46      | 0.8                           | 130     | COTS-Plus              | 3       |
| 100                        | 3.2     | 470                        | 4.12      | 0.9                           | 990     | Commercial             | 10      |
| 110                        | 3.7     | 680                        | 4.48      | 1                             | 5900    |                        |         |
| 120                        | 4.1     | 1200                       | 5.11      |                               |         |                        |         |
| 130                        | 4.6     | 2200                       | 5.87      |                               |         |                        |         |

\* $\pi_C = C/0.23$

| Environmental Factor $\pi_E$  |                |         | Series Resistance Factor $\pi_{SR}$ |            |
|-------------------------------|----------------|---------|-------------------------------------|------------|
| Environmental                 | $\pi_E$ Symbol | $\pi_E$ | Circuit Resistance (Ohms/Volt)      | $\pi_{SR}$ |
| Ground, Benign                | $G_B$          | 1       | > 0.8                               | 0.66       |
| Ground, Fixed                 | $G_F$          | 10      | > 0.6 to 0.8                        | 1          |
| Ground, Mobile                | $G_M$          | 20      | > 0.4 to 0.6                        | 1.3        |
| Naval, Sheltered              | $N_S$          | 7       | > 0.2 to 0.4                        | 2          |
| Naval, Unsheltered            | $N_U$          | 15      | > 0.1 to 0.2                        | 2.7        |
| Airborne, Inhabited Cargo     | $A_{IC}$       | 12      | 0 to 0.1                            | 3.3        |
| Airborne, Inhabited Fighter   | $A_{IF}$       | 15      |                                     |            |
| Airborne, Uninhabited Cargo   | $A_{UC}$       | 25      |                                     |            |
| Airborne, Uninhabited Fighter | $A_{UF}$       | 30      |                                     |            |
| Airborne, Rotary Winged       | $A_{RW}$       | 40      |                                     |            |
| Space, Flight                 | $S_F$          | 0.5     |                                     |            |
| Missile, Flight               | $M_F$          | 20      |                                     |            |
| Missile, Launch               | $M_L$          | 50      |                                     |            |
| Cannon, Launch                | $C_L$          | 570     |                                     |            |

More information for the definitions of the application environments can be seen in MIL-HDBK-217.

**Example Calculation: A 100 VDC 220μF COTS-Plus wet tantalum is being used in a fixed ground environment at 50°C with 60V applied and a series resistance of 0.2 Ohms/Volt.**

$$\begin{aligned} \pi_T &= 1.6 & \pi_C &= 3.46 \\ \pi_V &= 2 & \pi_{SR} &= 2 \\ \pi_Q &= 3 & \pi_E &= 10 \end{aligned}$$

$$\lambda_P = 0.0004 \times 1.6 \times 3.46 \times 2 \times 2 \times 3 \times 10 = 0.26$$

Failures/10<sup>6</sup> Hours

## 1.8 LONG TERM STORAGE

Higher temperature long term storage of completed circuit card assemblies with capacitors installed can result in an increase in direct current leakage (DCL). This will return to a normal level after a period of electrification. This may also occur during low temperature storage over an extended time period (typically several years). It is recommended that after such a storage period, capacitors should be powered by a soft start / slow voltage ramp to avoid damage to parts with elevated leakage current.

For such long term storage, it is recommended that capacitors are kept in environment below +40°C and powered every 2 years to keep the DCL at very low level for their entire life time.



## AMERICAS

**AVX Greenville, SC**  
Tel: 864-967-2150

## EUROPE

**AVX Limited, England**  
Tel: +44-1252-770000

**AVX S.A.S., France**  
Tel: +33-1-69-18-46-00

**AVX GmbH, Germany**  
Tel: +49-0811-95949-0

**AVX SRL, Italy**  
Tel: +39-02-614-571

**AVX Czech Republic**  
Tel: +420-57-57-57-521

**AVX/ELCO UK**  
Tel: +44-1638-675000

**ELCO Europe GmbH**  
Tel: +49-2741-299-0

**AVX S.A., Spain**  
Tel: +34-91-63-97-197

**AVX Benelux**  
Tel: +31-187-489-337

## ASIA-PACIFIC

**AVX/Japan**  
Tel: +81-740-32-1250

**AVX/Kyocera (S) Pte Ltd.,  
Singapore**  
Tel: +65-6286-7555

**AVX/Kyocera, Asia, Ltd.,  
Hong Kong**  
Tel: +852-2363-3303

**AVX/Kyocera Yuhan Hoesa,  
South Korea**  
Tel: +82-2785-6504

**AVX/Kyocera HK Ltd.,  
Taiwan**  
Tel: +886-2-2656-0258

**AVX/Kyocera (M) Sdn Bhd,  
Malaysia**  
Tel: +60-4228-1190

**AVX/Kyocera International  
Trading Co. Ltd.,  
Shanghai**  
Tel: +86-21-3255 1933

**AVX/Kyocera Asia Ltd.,  
Shenzen**  
Tel: +86-755-3336-0615

**AVX/Kyocera International  
Trading Co. Ltd.,  
Beijing**  
Tel: +86-10-6588-3528

**AVX/Kyocera India  
Liaison Office**  
Tel: +91-80-6450-0715

## ASIA-KED

(KYOCERA Electronic Devices)

**KED Hong Kong Ltd.**  
Tel: +852-2305-1080/1223

**KED Hong Kong Ltd.  
Shenzen**  
Tel: +86-755-3398-9600

**KED Company Ltd.  
Shanghai**  
Tel: +86-21-3255-1833

**KED Hong Kong Ltd.  
Beijing**  
Tel: +86-10-5869-4655

**KED Taiwan Ltd.**  
Tel: +886-2-2950-0268

**KED Korea Yuhan  
Hoesa, South Korea**  
Tel: +82-2-783-3604/6126

**KED (S) Pte Ltd.  
Singapore**  
Tel: +65-6509-0328

**Kyocera Corporation  
Japan**  
Tel: +81-75-604-3449

### Contact:

