

|                         |            |                  |            |
|-------------------------|------------|------------------|------------|
| MCT101E0TW1280800LMLIPS | 1280 x 800 | LVDS Interface   | TFT Module |
| <b>Specification</b>    |            |                  |            |
| Version: 1              |            | Date: 22/03/2018 |            |
| <b>Revision</b>         |            |                  |            |
| 1                       | 02/01/2018 | First issue.     |            |

| Display Features      |                           | <br><b>RoHS</b><br>compliant |
|-----------------------|---------------------------|---|
| Display Size          | 10.1"                     |   |
| Resolution            | 1280 x 800                |   |
| VGA Size              | WXGA                      |   |
| Orientation           | Landscape                 |   |
| Appearance            | RGB                       |   |
| Logic Voltage         | 3V                        |   |
| Interface             | LVDS                      |   |
| Brightness            | 250 cd/m <sup>2</sup>     |   |
| Touchscreen           | RTP                       |   |
| Module Size           | 229.34 x 148.98 x 4.80 mm |   |
| Operating Temperature | -20°C ~ +70°C             |   |
| Pinout                | 40 - Way FFC              |   |
|                       |                           | Box Quantity  |
|                       |                           | Weight / Display  |
|                       |                           | ---   |
|                       |                           | ---   |

| Display Accessories |  |
|---------------------|--|
| Part Number         | Description  |
| MPBV6               | 40 Way FFC to cable and wires.<br>Driven by any driver board that can be wired to a 1mm pitch SHDR-40V-S-B receptacle. |
| MCIB14/16           | HDMI-to-LVDS interface board, with voltage generation.   |
| LEDV3               | Constant current LED back light driver.  |

| Optional Variants                        |         |
|--|---------|
| Appearances                              | Voltage |
| Capacitive Touch Panel<br>No Touch Panel |         |



# **Contents**

- 1.Module Classification Information
- 2.Summary
- 3.General Specification
- 4.Interface
- 5.Contour Drawing
- 6.Absolute Maximum Ratings
- 7.Electrical Characteristics
- 8.Interface Timing Characteristics
- 9.Optical Characteristics
- 10.Reliability
- 11.Touch Panel Information
- 12.Other

MIDAS  
design • manufacture • supply



## **2.Summary**

TFT 10.1" is a IPS transmissive type color active matrix TFT liquid crystal display . In-Plane Switching (IPS) was one of the first refinements to produce significant gains in the light-transmissive characteristics of TFT panels. It is a technology that addresses the two main issues of a standard twisted nematic (TN) TFT display: colour and viewing angle.



design • manufacture • supply



### **3.General Specifications**

- Screen Diagonal: 10.1 inch
- Number of Pixels: 1280 x 3(R GB) x 800 dots
- Module dimension: 229.34 x 148.98 x 4.8 mm
- Active area: 216.96 (H) x 135.6(V) mm
- Pixel pitch: 0.1695 x 0.1695 mm
- Display Mode: Normally Black
- Pixel Arrangement: R.G.B. Vertical Stripe
- Backlight Type: LED, Normally White
- Aspect Ratio: 16:9
- Electrical Interface (Logic): LVDS
- With /Without TP: With RTP
- Surface: Anti-Glare

\*Color tone slight changed by temperature and driving voltage.

design • manufacture • supply



## 4. Interface

### Interface Connector

A 40pin connector is used for the module electronics interface. The recommended model is F62240-H1210B manufactured by Vigorconn.

| Pin No. | Symbol | I/O | Function                       | Remark                |
|---------|--------|-----|--------------------------------|-----------------------|
| 1       | VCOM   | P   | Common Voltage                 |                       |
| 2       | VDD    | P   | Power Supply                   |                       |
| 3       | VDD    | P   | Power Supply                   |                       |
| 4       | NC     | -   | No connection                  |                       |
| 5       | NC     | -   | No connection                  |                       |
| 6       | NC     | -   | No connection                  |                       |
| 7       | GND    | P   | Ground                         |                       |
| 8       | Rxin0- | I   | -LVDS Differential Data Input  | R0-R5,G0              |
| 9       | Rxin0+ | I   | +LVDS Differential Data Input  |                       |
| 10      | GND    | P   | Ground                         |                       |
| 11      | Rxin1- | I   | -LVDS Differential Data Input  | G1G5,B0,B1            |
| 12      | Rxin1+ | I   | +LVDS Differential Data Input  |                       |
| 13      | GND    | P   | Ground                         |                       |
| 14      | Rxin2- | I   | -LVDS Differential Data Input  | B2-B5,HS,VS,<br>DE    |
| 15      | Rxin2+ | I   | +LVDS Differential Data Input  |                       |
| 16      | GND    | P   | Ground                         |                       |
| 17      | RxCLK- | I   | -LVDS Differential Clock Input | LVDS CLK              |
| 18      | RxCLK+ | I   | +LVDS Differential Clock Input |                       |
| 19      | GND    | P   | Ground                         |                       |
| 20      | Rxin3- | I   | -LVDS Differential Data Input  | R6,R7,G6,G7,<br>B6,B7 |
| 21      | Rxin3+ | I   | +LVDS Differential Data Input  |                       |
| 22      | GND    | P   | Ground                         |                       |
| 23      | NC     | -   | No connection                  |                       |
| 24      | NC     | -   | No connection                  |                       |
| 25      | GND    | P   | Ground                         |                       |
| 26      | NC     | -   | No connection                  |                       |
| 27      | NC     | -   | No connection                  |                       |
| 28      | NC     | -   | No connection                  |                       |
| 29      | AVDD   | P   | Power for Analog Circuit       |                       |
| 30      | GND    | P   | Ground                         |                       |
| 31      | LED-   | P   | LED Cathode                    |                       |



|    |      |   |                  |  |
|----|------|---|------------------|--|
| 32 | LED- | P | LED Cathode      |  |
| 33 | NC   | - | No connection    |  |
| 34 | NC   | - | No connection    |  |
| 35 | VGL  | P | Gate OFF Voltage |  |
| 36 | NC   | - | No connection    |  |
| 37 | NC   | - | No connection    |  |
| 38 | VGH  | P | Gate ON Voltage  |  |
| 39 | LED+ | P | LED Anode        |  |
| 40 | LED+ | P | LED Anode        |  |


I: input, O: output, P: Power



design • manufacture • supply




## 5. Contour Drawing



design • manufacture • supply



| PIN NO. | SYMBOL | PIN NO. | SYMBOL  |
|---------|--------|---------|---------|
| 1       | VCOM   | 21      | Rxin3+  |
| 2       | VDD    | 22      | GND     |
| 3       | VDD    | 23      | NC      |
| 4       | NC     | 24      | NC      |
| 5       | NC     | 25      | GND     |
| 6       | NC     | 26      | NC      |
| 7       | GND    | 27      | LED_PWM |
| 8       | Rxin0- | 28      | NC      |
| 9       | Rxin0+ | 29      | AVDD    |
| 10      | GND    | 30      | GND     |
| 11      | Rxin1- | 31      | LED-    |
| 12      | Rxin1+ | 32      | LED-    |
| 13      | GND    | 33      | NC      |
| 14      | Rxin2- | 34      | NC      |
| 15      | Rxin2+ | 35      | VGL     |
| 16      | GND    | 36      | NC      |
| 17      | RxCLK- | 37      | CABC_EN |
| 18      | RxCLK+ | 38      | VGH     |
| 19      | GND    | 39      | LED+    |
| 20      | Rxin3- | 40      | LED+    |



The non-specified tolerance of dimension is

# MIDAS

design • manufacture • supply



## 6. Absolute Maximum Ratings

| Item                  | Symbol | Min | Typ | Max | Unit |
|-----------------------|--------|-----|-----|-----|------|
| Operating Temperature | TOP    | -20 | —   | +70 | °C   |
| Storage Temperature   | TST    | -20 | —   | +70 | °C   |

Note: Device is subject to be damaged permanently if stresses beyond those absolute maximum ratings listed above

1. Temp.  $\leq 60^{\circ}\text{C}$ , 90% RH MAX. Temp.  $> 60^{\circ}\text{C}$ , Absolute humidity shall be less than 90% RH at  $60^{\circ}\text{C}$

MIDAS

design • manufacture • supply



## 7.Electrical Characteristics


### 7.1. Typical Operation Conditions

(Note 1)

| Item                 | Symbol | Values |      |      | Unit | Remark |
|----------------------|--------|--------|------|------|------|--------|
|                      |        | Min.   | Typ. | MAX. |      |        |
| Power voltage        | VDD    | 2.3    | 2.5  | 2.7  | V    |        |
|                      | AVDD   | 8.0    | 8.2  | 8.4  | V    |        |
|                      | VGH    | 21.7   | 22   | 22.3 | V    |        |
|                      | VGL    | -7.3   | -7   | -6.7 | V    |        |
| Input signal voltage | VCOM   | 2.7    | 3.0  | 3.3  | V    | Note 2 |

Note 1: Be sure to apply VDD and VGL to the LCD first, and then apply VGH.

Note 2: Typical VCOM is only a reference value, it must be optimized according to each LCM.  
Be sure to use VR.




## 7.2. Current Consumption


| Item               | Symbol | Values |      |      | Unit | Remark     |
|--------------------|--------|--------|------|------|------|------------|
|                    |        | Min.   | Typ. | MAX. |      |            |
| Current for Driver | IGH    | -      | 705  | 750  | uA   | VGH = 22V  |
|                    | IGL    | -      | 705  | 750  | uA   | VGL = -7V  |
|                    | IVDD   | -      | 95   | 120  | mA   | VDD = 2.5V |
|                    | IAVDD  | -      | 45   | 70   | mA   | AVDD=8.2V  |

## 7.3. Power Sequence

a. Power on:




b. Power off:



#### 7.4. Backlight Characteristics

| Parameter                             | Symbol | Min.  | Typ. | Max. | Unit | Remark |
|---------------------------------------|--------|-------|------|------|------|--------|
| Supply voltage of white LED backlight | VL     | 8.6   | 9.6  | 10.2 | V    | Note 1 |
| Current for LED backlight             | IL     | —     | 220  | —    | mA   |        |
| LED life time                         | -      | 50000 | -    | -    | Hr   | Note 1 |

Note 1 : There are 1 Groups LED



Note 2 :  $T_a = 25 \text{ } ^\circ\text{C}$

Note 3 : Brightness to be decreased to 50% of the initial value

Note 4 : The single LED lamp case


design • manufacture • supply



## 8.LVDS Signal Timing Characteristics


### 8.1. AC Electrical Characteristics

| Parameter                                      | Symbol | Values |      |      | Unit | Remark         |
|--|--------|--------|------|------|------|----------------|
|  |        | Min.   | Typ. | MAX. |      |                |
| LVDS Differential input high Threshold voltage | RxVTH  | -      | -    | +100 | mV   | RXVCM=1.2<br>V |
| LVDS Differential input low Threshold voltage  | RxVTL  | -100   | -    | -    | mV   |                |
| LVDS Differential input common mode voltage    | RxVCM  | 0.7    | -    | 1.6  | V    |                |
| LVDS Differential voltage                      | VID    | 200    | -    | 600  | mV   |                |




## 8.2. Timing Table

| Parameter                         | Symbol          | Value |      |      | Unit | Remark           |
|-----------------------------------|-----------------|-------|------|------|------|------------------|
|                                   |                 | Min.  | Typ. | Max. |      |                  |
| Clock Frequency                   | 1/Tc            | 68.9  | 71.1 | 73.4 | Mhz  | Frame rate =60Hz |
| Horizontal display area           | thd             | 1280  |      |      | Tc   |                  |
| HS period time                    | th              | 1410  | 1440 | 1470 | Tc   |                  |
| HS Width +Back Porch +Front Porch | tHW+ tHBP +tHFP | 60    | 160  | 190  | Tc   |                  |
| Vertical display area             | tvd             | 800   |      |      | tH   |                  |
| VS period time                    | tv              | 815   | 823  | 833  | tH   |                  |
| VS Width +Back Porch +Front Porch | tvW+ tvBP +tvFP | 15    | 23   | 33   | tH   |                  |



### 8.3. LVDS Data Input Format



MIDAS

design • manufacture • supply



## 9.Optical Characteristics

| Item  | Symbol | Condition.                     | Min  | Typ. | Max. | Unit              | Remark            |  |
|---|--------|--------------------------------|------|------|------|-------------------|-------------------|--|
| Response time                                     | Tr     | $\theta=0^\circ, \phi=0^\circ$ | -    | 10   | 20   | .ms               | Note 3            |  |
|   | Tf     |                                | -    | 15   | 30   |                   |                   |  |
| Contrast ratio                                    | CR     | At optimized viewing angle     | 600  | 800  | -    | -                 | Note 4            |  |
| Color Chromaticity                                | White  | $\theta=0^\circ, \phi=0^\circ$ | 0.26 | 0.31 | 0.36 | -                 | Note 2,5          |  |
|   |        |                                | 0.28 | 0.33 | 0.38 | -                 |                   |  |
| Viewing angle<br>(Gray Scale Inversion Direction) | Hor.   | $CR \geq 10$                   | 75   | 85   | -    | Deg.              | Note 1            |  |
|   |        |                                | 75   | 85   | -    |                   |                   |  |
|   | Ver.   |                                | 75   | 85   | -    |                   |                   |  |
|   |        |                                | 75   | 85   | -    |                   |                   |  |
| Brightness  | -      | -                              | 250  | -    | -    | cd/m <sup>2</sup> | Center of display |  |

Ta=25±2°C

Note 1: Definition of viewing angle




Fig. 9.1. Definition of viewing angle

Note 2: Test equipment setup:

After stabilizing and leaving the panel alone at a driven temperature for 10 minutes, the measurement should be executed. Measurement should be executed in a stable, windless, and dark room. Optical specifications are measured by Topcon BM-7 or BM-5 luminance meter 1.0° field of view at a distance of 50cm and normal direction.





Fig. 9.2. Optical measurement system setup

Note 3: Definition of Response time:

The response time is defined as the LCD optical switching time interval between "White" state and "Black" state. Rise time,  $T_r$ , is the time between photo detector output intensity changed from 90% to 10%. And fall time,  $T_f$ , is the time between photo detector output intensity changed from 10% to 90%



Note 4: Definition of contrast ratio:

The contrast ratio is defined as the following expression.

$$\text{Contrast ratio (CR)} = \frac{\text{Luminance measured when LCD on the "White" state}}{\text{Luminance measured when LCD on the "Black" state}}$$

Note 5: White  $V_i = V_{i50} \pm 1.5V$

Black  $V_i = V_{i50} \pm 2.0V$

" $\pm$ " means that the analog input signal swings in phase with VCOM signal.

" $\pm$ " means that the analog input signal swings out of phase with VCOM signal.

The 100% transmission is defined as the transmission of LCD panel when all the input terminals of module are electrically opened.

Note 6: Definition of color chromaticity (CIE 1931)

Color coordinates measured at the center point of LCD


Note 7: Measured at the center area of the panel when all the input terminals of LCD panel are electrically opened.

design • manufacture • supply



## 10.Reliability

Content of Reliability Test (Wide temperature, -20°C~70°C)

| Environmental Test                   |   |   |      |
|--------------------------------------|---|---|------|
| Test Item                            | Content of Test   | Test Condition  | Note |
| High Temperature storage             | Endurance test applying the high storage temperature for a long time.   | 70°C<br>200hrs  | 2    |
| Low Temperature storage              | Endurance test applying the low storage temperature for a long time.  | -20°C<br>200hrs   | 1,2  |
| High Temperature Operation           | Endurance test applying the electric stress (Voltage & Current) and the thermal stress to the element for a long time.  | 70°C<br>200hrs  | —    |
| Low Temperature Operation            | Endurance test applying the electric stress under low temperature for a long time.  | -20°C<br>200hrs   | 1    |
| High Temperature/ Humidity Operation | The module should be allowed to stand at 60 °C,90%RH max  | 60°C,90%RH<br>96hrs   | 1,2  |
| Thermal shock resistance             | The sample should be allowed stand the following 10 cycles of operation<br><br><br>-20°C      25°C      70°C<br>30min      5min      30min<br>1 cycle | -20°C/70°C<br>10 cycles   | —    |
| Vibration test                       | Endurance test applying the vibration during transportation and using.  | Total fixed amplitude : 1.5mm<br>Vibration Frequency : 10~55Hz<br>One cycle 60 seconds to 3 directions of X,Y,Z for Each 15 minutes | 3    |
| Static electricity test              | Endurance test applying the electric stress to the terminal.  | VS=±600V(contact),<br>±800v(air),<br>RS=330Ω<br>CS=150pF<br>10 times  | —    |


Note1: No dew condensation to be observed.

Note2: The function test shall be conducted after 4 hours storage at the normal Temperature and humidity after remove from the test chamber.

Note3: The packing have to including into the vibration testing.



## 11.Touch Panel Information



design • manufacture • supply



### 11.1. Resistance Touch Panel General Specifications

| Item  | Description             |
|---|-------------------------|
| Driving condition                                   | DC5V                    |
| Operating force                                     | 20~100g                 |
| Linearity max                                       | $\leq \pm 1.5\%$        |
| Insulating resistance                               | >20MΩ , 25V(DC)         |
| Light transparency                                  | 70%                     |
| Structure type                                      | ITO Film/ITO Glass(F/G) |
| Surface Hardness                                    | 3H typ                  |
| Pen Hitting Durability<br>(with the silicon rubber) | >1000,000 times         |
| X resistance  | 450~1100Ω               |
| Y resistance  | 200~600Ω                |

MIDAS

design • manufacture • supply

