












02

Screwdrivers



Screwdrivers

	Kraftform Series 900	28
	Kraftform Series 300	35
	Kraftform Series Comfort	56
	Kraftform Series Classic	62
	Wooden Series	64
	Flagdriver, Stubby	66
	Accessories	68
	Kraftform Micro Series	71
	400 T-Handle Series	79
	VDE Tools Kraftform Series 100 Kraftform Kompakt VDE Kraftform Series Comfort VDE Kraftform Series Classic VDE	84
	ESD Tools	105

Kraftform Plus Series 900





Screwdrivers



Ever misused a screwdriver?

The Chiseldriver is the solution whenever the job requires more than just screwdriving. It is suitable for **fastening, chiselling** and **loosening seized screws or screw clamps**. The Wera Chiseldriver: the screwdriver you need when the going gets tough!



An integrated impact cap lengthens the service life and **reduces the danger of splintering**. Nevertheless, always wear protective goggles.



A hexagon blade made out of high-quality bit material extends right through the handle – thereby ensuring **full transfer of force**, even when struck with a hammer. The ductile tempered material **prevents the blade from splintering or breaking**.



Greater torque can be transferred by fitting an open-jaw or ring spanner over the integrated hex bolster.

The hard materials used for the handle ensure **rapid hand repositioning** without any danger of the skin "sticking" to the handle. The softer "anti-slip" zones provide increased grip, enabling the **low-loss transfer of high forces.**



The outstanding design of the Kraftform handle that fits perfectly into the hand. **Prevents hand injuries such as blisters and calluses. Wera Kraftform: a synonym for "graspable" ergonomics!**

The hexagonal non-roll feature **prevents any annoying rolling away** at the workplace.

Even **higher torque** can be transferred by connecting the square drive version to a T-handle, Zyklop ratchet or Bit Ratchet.

Kraftform Plus – Series 900

The chiseldriver for fastening and chiselling.

932 A Slotted screwdriver



Application: Slotted screws

Blade: Hexagonal throughout with impact cap, hexagonal bolster from 0.8 x 4.5

Design: Chrome-plated, Black Point

Handle: Kraftform with non-roll feature, multi-component, sizes 2.0 x 12.0, 2.5 x 14.0; Kraftform with non-roll feature, Weralit II, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05018260001	0,6	3,5	4		80	81	9/64"	3 1/8"	10
05018262001	0,8	4,5	5	8	90	98	0,178"	3 1/2"	10
05018264001	1,0	5,5	6	10	100	105	7/32"	4"	10
05018266001	1,2	7,0	6	10	125	105	9/32"	5"	10
05018268001	1,6	9,0	8	13	150	112	11/32"	6"	10
05018270001	1,6	10,0	8	13	175	112	3/8"	7"	5
05018272001	2,0	12,0	10	16	200	117	1/2"	8"	2
05018274001	2,5	14,0	10	16	250	117	9/16"	10"	2

932 AS Slotted screwdriver



Application: Slotted screws

Blade: Hexagonal throughout, impact cap with integrated square socket for insertion of 1/4" blades for higher torque, hexagonal bolster

Design: Chrome-plated, Black Point

Handle: Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05018300001	0,8	4,5	5	8	100	98	0,178"	4 3/64"	10
05018301001	1,0	5,5	6	10	103	105	7/32"	4 1/16"	10
05018302001	1,2	7,0	6	10	138	105	9/32"	5 7/16"	10



Can the screwdriver occasionally be struck with a hammer?



A screwdriver is very often misused, in that it is struck with a hammer for light chiselling jobs or for loosening rusted screws. This is dangerous because conventional screwdrivers are not appropriate for work of that kind – the grip and/or blade could splinter and cause injuries. The Wera Chiseldriver has been developed specifically for these applications. The head of the handle is fitted with a robust, metal impact cap which is directly connected to the hexagonal blade that extends right through the handle. The full force of hammer blows is thereby transferred. The special, ductile tempering of the blade prevents any splintering and injuries. Even more force can be transferred when screwdriving by fitting an open-jaw or ring spanner over the hex bolster.

The special, ductile tempering of the blade prevents any splintering and injuries. Even more force can be transferred when screwdriving by fitting an open-jaw or ring spanner over the hex bolster.

Impact cap with square drive, directly connected to the blade



Even higher torque can be transferred by connecting the square drive version to a T-handle, Zyklop ratchet or Bit Ratchet.

917 SPH Phillips screwdriver



Application: Phillips screws

Blade: Hexagonal throughout with impact cap, hexagonal bolster for sizes 1 - 4

Design: Chrome-plated, Black Point

Handle: Kraftform with non-roll feature, multi-component, size 4/200; Kraftform with non-roll feature, Weralit II, single-component

Code	mm	mm	mm	mm	mm	mm	mm
05017005001	PH 1	5	8	80	98	3 1/8"	10
05017010001	PH 2	6	10	100	105	4"	10
05017015001	PH 3	8	13	150	112	6"	5
05017020001	PH 4	10	16	200	117	8"	2

917 SPHS Phillips screwdriver

NEW



- Application:** Phillips screws
- Blade:** Hexagonal throughout, impact cap with integrated square socket for insertion of 1/4" blades for higher torque
- Design:** Chrome-plated, Black Point
- Handle:** Kraftform with non-roll feature, multi-component

Code	+	mm	mm	mm	mm	mm	mm
05017040001	PH 1	5	8	90	98	3 35/64"	10
05017041001	PH 2	6	10	113	105	4 29/64"	10

918 SPZ Screwdriver for Pozidriv screws



- Application:** Suitable for Pozidriv® screws
- Blade:** Hexagonal throughout with impact cap, hexagonal bolster for sizes 1 - 4
- Design:** Chrome-plated, Black Point
- Handle:** Kraftform with non-roll feature, multi-component, size 4/200; Kraftform with non-roll feature, Weralit II, single-component

Code	+	mm	mm	mm	mm	mm	mm
05017050001	PZ 1	5	8	80	98	3 1/8"	10
05017052001	PZ 2	6	10	100	105	4"	10
05017054001	PZ 3	8	13	150	112	6"	5
05017056001	PZ 4	10	16	200	117	8"	2

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

977 TORX® screwdriver



- Application:** TORX® socket screws
- Blade:** Hexagonal throughout with impact cap, hexagonal bolster
- Design:** Chrome-plated, Black Point
- Handle:** Kraftform with non-roll feature, multi-component

Code	TORX	mm	mm	mm	mm	mm	mm
05024400001	TX 15	5	8	80	98	3 1/8"	10
05024401001	TX 20	5	8	90	98	3 1/2"	10
05024402001	TX 25	6	10	100	105	4"	10
05024403001	TX 27	6	10	125	105	5"	10
05024404001	TX 30	8	13	150	112	6"	10
05024405001	TX 40	8	13	150	112	6"	10



Why is the Kraftform Plus handle made from several components?



Wera makes its Kraftform handles from several materials with different properties. The core is made from a hardwearing plastic that holds the blade securely even when subjected to great forces. The colour-coded soft zones of the external mantle consist of a softer material with more friction resistance for

high torque transfer. The black areas with a harder surface prevent the hand from sticking to the handle enabling you to adjust your grip more quickly.

How can I prevent blisters on my hands?



Manual screwdriving can be quite painful work. Wera has developed the Kraftform handle with a shape that fits snugly in the hand. An optimum positive fit between the hand and the handle and the choice of materials prevent blisters, calluses and excessive strain. You'll notice the difference, especially when repositioning your hand on the handle.

Kraftform Plus – Series 900

The chiseldriver for fastening and chiselling.

932/6 Screwdriver set Kraftform Wera: Chiseldriver and rack



Application: Slotted and Phillips screws
Content: 6-piece set and rack in display carton

Code				
05018282001	+	917 SPH	1 x PH 1x80; 1 x PH 2x100	1
	-	932 A	1 x 0,6x3,5x80; 1 x 0,8x4,5x90; 1 x 1,0x5,5x100; 1 x 1,2x7,0x125	

932 S/6 Screwdriver set Kraftform Wera: Chiseldriver and rack



NEW



Application: Slotted and Phillips screws, impact cap with integrated square socket for insertion of 1/4" blades for higher torque
Content: 6-piece set and rack in display carton

Code				
05018283001	+	917 SPHS	1 x PH 1x90; 1 x PH 2x113	1
	-	932 A	1 x 0,6x3,5x80	
	-	932 AS	1 x 0,8x4,5x100; 1 x 1,0x5,5x103; 1 x 1,2x7,0x138	

932/918/6 Screwdriver set Kraftform Wera: Chiseldriver and rack



Application: Slotted and Pozidriv[®] screws
Content: 6-piece set and rack in display carton

Code				
05018287001	+	918 SPZ	1 x PZ 1x80; 1 x PZ 2x100	1
	-	932 A	1 x 0,6x3,5x80; 1 x 0,8x4,5x90; 1 x 1,0x5,5x100; 1 x 1,2x7,0x125	

977/6 TORX[®] Screwdriver set Kraftform Wera: Chiseldriver and rack



Application: TORX[®]
Content: 6-piece set and rack in display carton

Code				
05024410001	+	977 TORX [®]	1 x TX 15x80; 1 x TX 20x90; 1 x TX 25x100; 1 x TX 27x125; 1 x TX 30x150; 1 x TX 40x150	1

^{*)} Pozidriv = reg. trademark of European Industrial Service Ltd.

Kraftform Plus Series 300



Screwdrivers



Ever worked in a truly ergonomic manner?

Kraftform Plus prevents injuries – even long-term.

Kraftform Plus screwdrivers enable a **higher transfer of force** with **less effort** and relieve the entire hand-arm system – even with **intensive use**. Combined with other technical and practical product advantages such as the **Lasertip** for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice for manual screwdriving jobs.







The basic idea for the prototype of the Kraftform handle – that the **hand** should dictate the **design** – has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer-Institut, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

The outstanding design of the Kraftform handle that fits perfectly into the hand **prevents hand injuries such as blisters and calluses**.

The hard materials used for the handle ensure **rapid hand repositioning** without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.



The large contact area – with particularly high friction to the soft zones – results in **high torque transfer without any bruising from the edges**.

The Kraftform handle functions superbly in all application situations, and it really has to. The application environment often does not allow any direct tool access.


Wera Lasertip "bites" itself into the screw head and **prevents any slips out** of the recess. It can be used for slotted, Phillips and Pozidriv® screws.

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

A precisely-focused laser creates a sharp-edged surface structure. This laser treatment results in an edge hardness of up to 1000 HV 0.3.




Wera Lasertip **reduces the contact pressure required and enhances force transfer** - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.



The screw symbol and tip size identification markings on the handle **make it easier to find** the right screwdriver in the tool case or at the workplace.



The hexagonal non-roll feature **prevents any rolling away** at the workplace.



The Wera TORX® HF profile (HF = Holding Function) securely holds TORX® screws on the tool tip thanks to its drive geometry and the wedging forces associated with this. Ideal for work in difficult-to-access areas e.g. screw connections in deep blind holes.





The Wera Hex-Plus profile with its improved geometry **prevents damage** to the heads of hexagonal socket screws. A higher torque transfer of up to 20 % is possible. This also makes screwdriving safer and more convenient.



Lasertip



Lasertip is also ideal for **oily and greasy** applications, circumstances that would otherwise favour the slipping out of the tool from the screw.




The screwdriver sets are always supplied with a wall-mountable rack. This ensures **organised storage** and **quick access**. The rack is also available as an individual item.

Kraftform Plus – Series 300

The right tool for every application

335 Slotted screwdriver



Application: Slotted screws

Blade: Round

Design: Chrome-plated, Lasertip

Handle: Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
0500806001 ¹⁾	0,4	2,0	60	70	2,5	5/64"	2 3/8"	10
0511000001 ¹⁾	0,4	2,5	60	70	2,5	3/32"	2 3/8"	10
0500807001 ¹⁾	0,4	2,5	75	70	2,5	3/32"	3"	10
0500808001 ¹⁾	0,5	3,0	150	81	4,0	1/8"	6"	10
0500809001 ¹⁾	0,5	3,0	200	81	4,0	1/8"	8"	5
05110001001 ¹⁾	0,5	3,0	80	81	3,0	1/8"	3 1/8"	10
05008015001	0,6	3,5	100	81	3,5	9/64"	4"	10
05110002001	0,6	3,5	125	81	3,5	9/64"	5"	10
05110003001	0,6	3,5	200	81	3,5	9/64"	8"	5
05110004001	0,8	4,0	100	98	4,0	5/32"	4"	10
05110005001	0,8	4,0	150	98	4,0	5/32"	6"	10
05110006001	0,8	4,0	200	98	4,0	5/32"	8"	5
05008027001 ¹⁾	0,8	4,0	300	98	4,0	5/32"	12"	2
05110007001	1,0	5,5	125	98	5,5	7/32"	5"	10
05008055001	1,0	5,5	150	98	5,5	7/32"	6"	10
05110008001	1,0	5,5	200	98	5,5	7/32"	8"	5
05008060001 ¹⁾	1,0	5,5	300	98	5,5	7/32"	12"	2
05008061001	1,2	6,0	100	105	6,0	5/16"	4"	10

1) without Lasertip

334 SK Slotted screwdriver



Application: Slotted screws


Blade: Hexagonal with bolster from 0.8 x 4.5

Design: Chrome-plated, Lasertip

Handle: Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	
05007670001	0,6	3,5	4	-	75	81	9/64"	3"	10
05007671001	0,8	4,0	4	-	90	81	5/32"	3 1/2"	10
05007672001	0,8	4,5	5	8	90	98	0,178"	3 1/2"	10
05007673001	1,0	5,5	6	10	100	98	7/32"	4"	10
05007674001	1,2	6,5	6	10	125	105	1/4"	5"	10
05007675001	1,2	7,0	6	10	125	105	9/32"	5"	10
05007676001	1,6	9,0	8	13	150	112	11/32"	6"	10
05007677001	1,6	10,0	8	13	175	112	3/8"	7"	5

334 Slotted screwdriver



Application: Slotted screws

Blade: Round

Design: Chrome-plated, Lasertip


Handle: Kraftform with non-roll feature, multi-component, sizes 2.0 x 12.0, 2.5 x 14.0; Kraftform with non-roll feature, Weralit II, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05007610001	0,8	5,0	100	98	5,0	3/16"	4"	10
05007620001	1,0	6,0	125	105	6,0	1/4"	5"	10
05340330001	1,0	6,0	150	105	6,0	1/4"	6"	10
05110010001	1,2	6,5	150	105	6,0	1/4"	6"	10
05007635001	1,2	7,0	150	105	7,0	9/32"	6"	10
05007621001	1,2	6,5	200	105	7,0	9/32"	8"	5
05110011001	1,2	8,0	175	112	7,0	5/16"	7"	5
05007640001	1,6	8,0	175	112	7,0	5/16"	7"	5
05110104001	1,6	10,0	200	112	9,0	3/8"	8"	5
05110105001 ¹⁾	2,0	12,0	250	117	10,0	1/2"	10"	2
05018274001	2,5	14,0	250	117	16,0	9/16"	10"	2

1) without Lasertip



How to prevent the screwdriver from slipping out of the screw head



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.



378 B Slotted screwdriver



- Application:** Slotted screws
- Blade:** Square as bolster
- Design:** Chrome-plated, Black Point
- Handle:** Kraftform with non-roll feature, multi-component, sizes 2.0 x 12.0 x 250, 2.5 x 14.0 x 225; Kraftform with non-roll feature, Weralit II, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05110050001	0,8	4,0	4	75	98	5/32"	3"	10
05110051001	1,0	5,5	5	100	98	7/32"	4"	10
05110052001	1,2	6,5	6	125	105	1/4"	5"	10
05110053001	1,6	8,0	8	150	112	5/16"	6"	10
05007355001	1,6	10,0	8	60	112	3/8"	2 3/8"	5
05110054001	1,6	10,0	8	175	112	3/8"	7"	5
05110150001	1,6	10,0	8	200	112	3/8"	8"	5
05007360001	1,6	10,0	8	600	112	3/8"	24"	5
05110055001	2,0	12,0	10	200	112	1/2"	8"	5
05110151001	2,0	12,0	10	250	112	1/2"	10"	5
05110056001	2,5	14,0	12	225	117	9/16"	9"	5

335 FK Slotted screwdriver




- Application:** Actuating tool for spring-loaded terminal blocks in switch cabinet construction
- Blade:** Round
- Design:** Chrome-plated, Black Point
- Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05008069001	0,4	2,5	75	98	2,5	5/64"	3"	10
05008070001	0,6	3,5	100	81	3,5	9/64"	4"	10
05008075001	0,8	4,0	100	98	4,0	5/64"	4"	10
05008080001	1,0	5,5	150	98	5,5	7/32"	6"	10



How to avoid bruising and injuries to the hands



Screwdriving by hand can actually be quite painful, particularly during extended use. Wera developed the Kraftform handle with this in mind. Its design fits exactly to the hand, and this ergonomic handle, which perfectly fits the hand, and the materials used combine to prevent blisters, calluses and strain. This is particularly noticeable when changing the position of grip. This makes the concept of ergonomics "graspable".



Why is the Kraftform Plus handle made from several components?



Wera makes its Kraftform handles from several materials with different properties. The core is made from a hardwearing plastic that holds the blade securely even when subjected to great forces. The colour-coded soft zones of the external mantle

consist of a softer material with more friction resistance for high torque transfer. The black areas with a harder surface prevent the hand from sticking to the handle enabling you to adjust your grip more quickly.



350 SK PH Screwdriver for Phillips screws



- Application:** Phillips screws
- Blade:** Hexagonal, sizes 1 - 3 with bolster
- Design:** Chrome-plated, Lasertip
- Handle:** Kraftform with non-roll feature, multi-component

Code	+	mm	mm	mm	mm	mm	mm	mm
05008750001 ¹⁾	PH 0	4		60	81	2 3/8"		5
05008751001	PH 1	5	8	80	98	3 1/8"		10
05008752001	PH 2	6	10	100	105	4"		10
05008753001	PH 3	8	13	150	112	6"		5

1) without Lasertip

355 PZ Screwdriver for Pozidriv screws



- Application:** Suitable for Pozidriv[®] screws
- Blade:** Round
- Design:** Chrome-plated, Lasertip
- Handle:** Kraftform with non-roll feature, multi-component


Code	mm	mm	mm	mm	mm	mm
05009305001 ¹⁾	PZ 0	60	81	3,0	2 3/8"	10
05009310001	PZ 1	80	98	4,5	3 1/8"	10
05009312001	PZ 1	200	98	4,5	8"	2
05009313001 ¹⁾	PZ 1	300	98	4,5	12"	2
05009315001	PZ 2	100	105	6,0	4"	10
05009317001	PZ 2	200	105	6,0	8"	2
05347743001	PZ 2	250	105	6,0	10"	2
05009319001 ¹⁾	PZ 2	300	105	6,0	12"	2
05009320001	PZ 3	150	112	8,0	6"	5
05009325001 ¹⁾	PZ 4	200	112	10,0	8"	2

1) without Lasertip

^{*)} Pozidriv = reg. trademark of European Industrial Service Ltd.



How to prevent the screwdriver from slipping out of the screw head



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.

352 Ball end screwdriver for hexagon socket screws



Application: Hexagon socket screws
Blade: Hexagonal
Design: Ball end hexagon, chrome-plated, Black Point
Handle: Kraftform with non-roll feature, multi-component, sizes W/F 12.0, W/F 1/2"; Kraftform with non-roll feature, Weralit II, single-component



Code	mm	mm	mm	mm	mm	
05022795001	1,5		60	70	2 3/8"	10
05022800001	2,0		100	70	4"	10
05138070001	2,5		100	81	4"	10
05022805001	3,0		100	81	4"	10
05022810001	4,0		100	98	4"	10
05022815001	5,0		100	105	4"	10
05022820001	6,0		125	105	5"	5
05022825001	8,0		150	112	6"	5
05022830001	10,0		150	112	6"	5
05022835001	12,0		150	117	6"	5
05022905001		5/32"	100	98	4"	5
05022910001		3/16"	100	105	4"	5
05022915001		7/32"	100	105	4"	5
05022920001		1/4"	125	105	5"	5
05022925001		5/16"	150	112	6"	5
05022930001		3/8"	150	112	6"	5
05022935001		1/2"	150	117	6"	5

TORX® ball tip and hexagon ball tip



The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs. This ball tip geometry – often found on L-keys – is now available on a number of Wera bits.

367 TORX® HF screwdriver with holding function




Application: TORX® socket screws
Blade: Round
Design: Holding function for TORX® screws made according to Acument Global Technologies Inc. specifications, chrome-plated
Handle: Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	
05028048001	TX 8	60	81	3,5	2 3/8"	10
05028049001	TX 9	60	81	4,0	2 3/8"	10
05028050001	TX 10	80	81	4,0	3 1/8"	10
05028051001	TX 15	80	98	4,0	3 1/8"	10
05028052001	TX 20	100	98	4,5	4"	10
05028053001	TX 25	100	105	5,0	4"	10
05028054001	TX 27	115	105	5,5	4 9/16"	10
05028055001	TX 30	115	105	6,0	4 9/16"	10
05028056001	TX 40	130	112	7,0	5 3/16"	10



What is the purpose of the TORX® HF profile?



In tight assembly or disassembly situations, for example in engine compartments, it is not possible to securely hold the screw with the hand on the screwdriver, and the screw subsequently often gets lost. Lengthy searches or the loss of the screw (with the associated danger that could bring about) are the consequence. The TORX® HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that the screw is securely held on the tool!

Kraftform Plus – Series 300

The right tool for every application

367 TORX® HF screwdriver with holding function



Application: TORX® socket screws
Blade: Round
Design: Holding function for TORX® screws made according to Acument Global Technologies Inc. specifications, chrome-plated, extra long blade to enable work on low-down, difficult to access screws
Handle: Kraftform with non-roll feature, multi-component

Code	TORX	mm	mm	mm	mm	mm	mm
05028070001	TX 20	300	98	4,5	12"		4
05028071001	TX 25	300	105	6,0	12"		4
05028072001	TX 27	300	105	6,0	12"		4
05028073001	TX 30	300	105	6,0	12"		4

367 K Ball end TORX® screwdriver



Application: TORX® socket screws
Blade: Round
Design: Ball end, chrome-plated, Black Point
Handle: Kraftform with non-roll feature, multi-component

Code	TORX	mm	mm	mm	mm	mm	mm
05027950001	TX 15	80	98	4,0	3 1/8"		5
05027952001	TX 20	100	98	4,5	4"		5
05027954001	TX 25	100	105	5,0	4"		5
05027956001	TX 27	115	105	5,5	4 9/16"		5
05027958001	TX 30	115	105	6,0	4 9/16"		5
05027960001	TX 40	130	112	7,0	5 3/16"		5
05027962001	TX 45	130	112	8,0	5 3/16"		5

367 TORX® screwdriver



Application: TORX® socket screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform with non-roll feature, multi-component

Code	TORX	mm	mm	mm	mm	mm	mm
05028000001	TX 5	60	70	3,5	2 3/8"		10
05028001001	TX 6	60	70	3,5	2 3/8"		10
05028002001	TX 7	60	70	3,5	2 3/8"		10
05028003001	TX 8	60	81	3,5	2 3/8"		10
05028004001	TX 9	60	81	4,0	2 3/8"		10
05028005001	TX 10	80	81	4,0	3 1/8"		10
05028008001	TX 15	80	98	4,0	3 1/8"		10
05028010001	TX 20	100	98	4,5	4"		10
05028012001	TX 25	100	105	5,0	4"		10
05028013001	TX 27	115	105	5,5	4 9/16"		10
05028015001	TX 30	115	105	6,0	4 9/16"		10
05028020001	TX 40	130	112	7,0	5 1/8"		10
05028025001	TX 45	130	112	8,0	5 1/8"		10



TORX® with borehole



TORX® tools with a borehole prevent the unauthorised unfastening of safety screws. The screws contain a pin that protrudes into the drive profile so that "normal" TORX® tools cannot be used. This pin fits into the borehole of TORX® B0 tools allowing safety screws to be unfastened.

367 TORX® BO screwdriver



Application: TORX® screws with safety pin
(BO = with bore hole)

Blade: Round

Design: Bore hole in TORX® section, chrome-plated, Black Point

Handle: Kraffform with non-roll feature, multi-component

Code	TORX	mm	mm	mm	mm	mm	mm
05138257001	TX 7	60	70	3,5	2 3/8"		5
05138258001	TX 8	60	81	3,5	2 3/8"		5
05138259001	TX 9	60	81	4,0	2 3/8"		5
05138267001	TX 9	300	81	4,0	12"		5
05138260001	TX 10	80	81	4,0	3 1/8"		5
05138268001	TX 10	300	81	4,0	12"		5
05138261001	TX 15	80	98	4,0	3 1/8"		5
05138269001	TX 15	300	98	4,0	12"		2
05138262001	TX 20	100	98	4,5	4"		5
05138270001	TX 20	300	98	4,5	12"		2
05138263001	TX 25	100	105	5,0	4"		5
05138264001	TX 27	115	105	5,5	4 9/16"		5
05138265001	TX 30	115	105	6,0	4 9/16"		5
05138266001	TX 40	130	112	7,0	5 3/16"		5

367 TORX PLUS® screwdriver



Application: TORX PLUS® socket screws


Blade: Round

Design: Chrome-plated, Black Point

Handle: Kraffform with non-roll feature, multi-component

Code	TORX PLUS	mm	mm	mm	mm	mm	mm
05028029001	5 IP	60	70	3,5	2 3/8"		5
05028030001	6 IP	60	70	3,5	2 3/8"		5
05028031001	7 IP	60	70	3,5	2 3/8"		5
05028032001	8 IP	60	70	3,5	2 3/8"		5
05028033001	9 IP	60	81	4,0	2 3/8"		5
05028034001	10 IP	80	81	4,0	3 1/8"		5
05028035001	15 IP	80	98	4,0	3 1/8"		5
05028036001	20 IP	100	98	4,5	4"		5
05028037001	25 IP	100	105	5,0	4"		5
05028028001	27 IP	115	105	5,5	4 9/16"		5
05028038001	30 IP	115	105	6,0	4 9/16"		5
05028039001	40 IP	130	112	7,0	5 3/16"		5

TORX PLUS®




Compared with the "normal" TORX® profile, the elliptical instead of circular profile enlarges the 6 flanks that transfer torque between the tool and the screw. This means that the force applied when screwdriving is spread across a larger surface area. Higher torque is transferred and, in addition, the service life of the screw and tool are lengthened. The so-called centre-lock screws on cutting tools represent a typical use of this type of screw profile. The thermal influences on such holders for carbide insert tips often "bake" the retaining screws so firmly that it is important to have a profile that considerably enhances the loosening torque capability of the screws. For this reason a torque-stable screw profile is necessary to avoid any possible damage to the screw and to exclude the possibility of an otherwise costly machine downtime.

Kraftform Plus – Series 300

The right tool for every application

371 TORQ-SET® Mplus screwdriver



Application: TORQ-SET® screws

Blade: Round

Design: Mplus for higher breaking torque and longer service life, chrome-plated

Handle: Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	
05028130001	6	80	98	4,5	3 1/8"		5
05028132001	8	100	105	6,0	4"		5
05028134001	10	100	105	6,0	4"		5
05028136001	1/4"	125	112	8,0	5"		5

368 Screwdriver for square socket head screws



Application: Square socket screws

Blade: Round


Design: Chrome-plated, Black Point except for sizes 01+02

Handle: Kraftform with non-roll feature, multi-component, # 2/300, # 01/25, # 02/25; Weralit II, single-component

Code		mm	mm	mm	mm	mm	
05117680001	# 00	60	81	3,5	2 3/8"		5
05117681001	# 0	60	81	4,0	2 3/8"		5
05117682001	# 1	80	98	4,5	3 1/8"		5
05117683001	# 1	200	98	4,5	8"		5
05117684001	# 2	100	105	6,0	4"		5
05117685001	# 2	200	105	6,0	8"		5
05117691001	# 2	300	105	6,0	12"		2
05117686001	# 3	150	112	8,0	6"		5
05117687001	# 4	200	112	8,0	8"		5
05117688001	# 01	25	54	4,5	1"		5
05117689001	# 02	25	54	6,0	1"		5



How can I prevent frequent breakages of TORQ-SET® bits?



Wera developed the Mplus profile with stronger flanks compared with tools with a conventional TORQ-SET® profile. This results in approximately 70 % extra torsional strength and greatly extends the service life of Wera Mplus tools.

375 TRI-WING® screwdriver



Application: TRI-WING® screws

Blade: Round

Design: Chrome-plated, Black Point

Handle: Kraftform with non-roll feature, multi-component

Code		mm	mm	mm	mm	mm	
05028116001	0	80	81	3,5	3 1/8"		5
05028118001	1	80	81	3,5	3 1/8"		5
05028120001	2	80	98	4,5	3 1/8"		5
05028122001	3	80	98	4,5	3 1/8"		5
05028124001	4	100	98	6,0	4"		5
05028126001	5	100	98	6,0	4"		5

391 Hose clamp screwdriver



- Application:** Hexagon headed bolts, screws and nuts
- Blade:** Round, flexible
- Design:** Nutdriver for hexagon head bolts
- Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm
05028148001	6	167	98	6 9/16"		5
05028150001	7	167	98	6 9/16"		5
05028152001	8	167	98	6 9/16"		5

395 Nutdriver




- Application:** Hexagon headed bolts, screws and nuts
- Blade:** Round
- Design:** Chrome-plated, nutdriver for hexagon head bolts
- Handle:** Kraftform with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm
05028205001	3,0	125	98	5,0	5"	5
05028210001	3,5	125	98	6,1	5"	5
05028215001	4,0	125	98	6,9	5"	5
05028220001	4,5	125	98	7,1	5"	5
05028225001	5,0	125	98	8,1	5"	5
05028230001	5,5	125	98	8,1	5"	5
05029405001	6,0	125	98	9,1	5"	5
05029410001	7,0	125	105	11,0	5"	5
05029415001	8,0	125	105	12,1	5"	5
05029420001	9,0	125	105	13,1	5"	5
05029425001	10,0	125	112	14,1	5"	5
05029430001	11,0	125	112	16,0	5"	5
05029435001	12,0	125	112	17,1	5"	5
05029440001	13,0	125	112	18,1	5"	5
05029445001	14,0	125	112	19,1	5"	5
05029450001	15,0	125	112	21,0	5"	5



How to avoid bruising and injuries to the hands



Screwdriving by hand can actually be quite painful, particularly during extended use. Wera developed the Kraftform handle with this in mind. Its design fits exactly to the hand, and this ergonomic handle, which perfectly fits the hand, and the materials used combine to prevent blisters, calluses and strain. This is particularly noticeable when changing the position of grip. This makes the concept of ergonomics "graspable".

Kraftform Plus – Series 300

The right tool for every application

395 HO Nutdriver



- Application:** Hexagon headed bolts, screws and nuts
Blade: Round
Design: Hollow shaft for protruding threaded rods, chrome-plated
Handle: Kraftform with non-roll feature, multi-component
TIP: **The hollow shaft enables seized screws or those on long threads to be tightened and loosened**

Code	mm	mm	mm	mm	mm	
05029460001	5,0	70	98	7,2	2 25/32"	5
05029461001	5,5	70	98	7,2	2 25/32"	5
05029462001	6,0	70	98	7,2	2 25/32"	5
05029463001	7,0	80	105	7,2	3 5/32"	5
05029464001	8,0	80	105	9,3	3 5/32"	5
05029465001	10,0	80	112	9,3	3 5/32"	5
05029466001	13,0	80	112	11,0	3 5/32"	5

395 HO Nutdriver, imperial




- Application:** Hexagon headed bolts, screws and nuts
Blade: Round
Design: Chrome-plated, hollow shaft for protruding threaded rods
Handle: Kraftform with non-roll feature, multi-component
TIP: **The hollow shaft enables seized screws or those on long threads to be tightened and loosened**

Code	mm	mm	mm	mm	mm	
05029501001	3/16"	70	98	7,2	2 25/32"	5
05029502001	1/4"	70	98	7,2	2 25/32"	5
05029503001	5/16"	80	105	9,3	3 5/32"	5
05029504001	11/32"	80	105	9,3	3 5/32"	5
05029505001	3/8"	80	112	9,3	3 5/32"	5
05029506001	7/16"	80	112	11,0	3 5/32"	5
05029507001	1/2"	80	112	11,0	3 5/32"	5




What is the purpose of a screwdriver with hollow shaft?



A screwdriver with a hollow shaft is needed whenever there are screwdriving jobs involving threaded rods i.e. the threaded rod through the nut can slip into the hollow shaft of the screwdriver.



334/6 Rack screwdriver set Kraffform Plus Lasertip and rack



Lasertip round blades and rack


Application: Slotted and Phillips screws

Content: 6-piece set and rack in display carton

Code			
05105650001	● 334	1 x 1,2x6,5x150	1
	● 335	1 x 0,5x3,0x80 ¹⁾ ; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	⊕ 350 PH	1 x PH 1x80; 1 x PH 2x100	

1) without Lasertip

334/355/6 Rack screwdriver set Kraffform Plus Lasertip and rack



Lasertip round blades and rack

Application: Slotted and Pozidriv[®] screws

Content: 6-piece set and rack in display carton

Code			
05105656001	● 334	1 x 1,2x6,5x150	1
	● 335	1 x 0,5x3,0x80 ¹⁾ ; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	⊕ 355 PZ	1 x PZ 1x80; 1 x PZ 2x100	

1) without Lasertip

^{*)} Pozidriv = reg. trademark of European Industrial Service Ltd.

334 SK/6 Rack screwdriver set Kraffform Plus Lasertip and rack



Lasertip hexagon blades and rack

Application: Slotted and Phillips screws

Content: 6-piece set and rack in display carton

Code			
05007680001	● 334 SK	1 x 0,6x3,5x75; 1 x 0,8x4,0x90; 1 x 1,0x5,5x100; 1 x 1,2x6,5x125	1
	⊕ 350 SK PH	1 x PH 1x80; 1 x PH 2x100	

Kraftform Plus – Series 300

The right tool for every application

334/355 SK/6 Screwdriver set Kraftform Plus Lasertip and rack



Lasertip hexagonal blades and rack

Application: Slotted and Pozidriv* screws

Content: 6-piece set and rack in display carton

Code			
05007681001	● 334 SK	1 x 0,6x3,5x75; 1 x 0,8x4,0x90; 1 x 1,0x5,5x100; 1 x 1,2x6,5x125	1
	⊕ 355 SK PZ	1 x PZ 1x80; 1 x PZ 2x100	

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

335/350/367/7 Rack screwdriver set Kraftform Plus Lasertip and rack



Lasertip round blades and rack

Application: Slotted, cross, Phillips-Recess, Pozidriv* and TORX® screws

Content: 7-piece set and rack in display carton

Code			
05320540001	● 335	1 x 0,8x4,0x100	1
	⊕ 350 PH	1 x PH 2x100	
	⊕ 355 PZ	1 x PZ 1x80; 1 x PZ 2x100	
	⊕ 367 TORX®	1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100	

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

335/350/355/6 Screwdriver set Kraftform Plus Lasertip and rack



Lasertip blades and rack

Application: Slotted, Phillips and Pozidriv* screws

Content: 6-piece set and rack in display carton

Code			
05105622001	● 335	1 x 0,8x4,0x100; 1 x 1,0x5,5x125	1
	⊕ 350 PH	1 x PH 1x80; 1 x PH 2x100	
	⊕ 355 PZ	1 x PZ 1x80; 1 x PZ 2x100	


*) Pozidriv = reg. trademark of European Industrial Service Ltd.

? Why is the Kraftform Plus handle made out of several components?



Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely, even under high strain. A softer material is used for the coloured soft zones, which has a high frictional resistance and allows the transfer of high forces - thus requiring less screwdriving effort. The black sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

367/7 TORX® HF Kraftform Plus screwdriver set with holding function and rack



Application: TORX®

Content: 7-piece set and rack in display carton

Code			
05223161001	367 TORX® HF	1 x TX 8x60; 1 x TX 10x80; 1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100; 1 x TX 27x115; 1 x TX 30x115	1

367/6 TORX® HF Kraftform Plus screwdriver set with holding function and rack



Application: TORX®

Content: 6-piece set and rack in display carton

Code			
05028059001	367 TORX® HF	1 x TX 10x80; 1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100; 1 x TX 30x115; 1 x TX 40x130	1

367/4 TORX® HF Kraftform Plus screwdriver set with holding function and 300mm-long blades




Application: TORX® with holding function, extra long (300 mm) blade

Content: 4-piece set

Code			
05028074001	367 TORX HF L	1 x TX 20x300; 1 x TX 25x300; 1 x TX 27x300; 1 x TX 30x300	1



What is the purpose of the TORX® HF profile?



In tight assembly or disassembly situations, for example in engine compartments, it is not possible to securely hold the screw with the hand on the screwdriver, and the screw subsequently often gets lost. Lengthy searches or the loss of the

screw (with the associated danger that could bring about) are the consequence. The TORX® HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that the screw is securely held on the tool!

Kraftform Plus – Series 300

The right tool for every application

367/6 TORX® BO Kraftform Plus TORX® safety screwdriver set and rack




Application: TORX® screws with safety pin (BO = with bore hole)

Content: 6-piece set and rack in display carton

Code			
05138250001	♻️	367 TORX® BO	1 x TX 10x80; 1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100; 1 x TX 30x115; 1 x TX 40x130



TORX® with borehole



TORX® tools with a borehole prevent the unauthorised unfastening of safety screws. The screws contain a pin that protrudes into the drive profile so that "normal" TORX® tools cannot be used. This pin fits into the borehole of TORX® BO tools allowing safety screws to be unfastened.

367/6 Screwdriver set Kraftform Plus TORX® and rack



Application: TORX®

Content: 6-piece set and rack in display carton

Code			
05028062001	♻️	367 TORX®	1 x TX 10x80; 1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100; 1 x TX 30x115; 1 x TX 40x130

395 H0/7 SM Nutdriver set




Application: Hexagon headed bolts, screws and nuts

Content: 7-piece set in display carton

Code			
05029510001	● 395 H0	1 x 5,0x70; 1 x 5,5x70; 1 x 6,0x70; 1 x 7,0x80; 1 x 8,0x80; 1 x 10,0x80; 1 x 13,0x80	1



What is the purpose of a screwdriver with hollow shaft?



A screwdriver with a hollow shaft is needed whenever there are screwdriving jobs involving threaded rods i.e. the threaded rod through the nut can slip into the hollow shaft of the screwdriver.

Kraftform XXL



12-piece screwdriver set for all-round applications

Code			
05051010001	● 160 i VDE	1 x 0,4x2,5x80 ¹⁾ ; 1 x 0,6x3,5x100	1
	● 247	1 x 0,5x3,0x70	
	● 334	1 x 1,2x6,5x150	
	● 335	1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	⊕ 350 PH	1 x PH 1x80; 1 x PH 2x100	
	⊕ 355 PZ	1 x PZ 1x80; 1 x PZ 2x100	
	● 932 A	1 x 1,0x5,5x100; 1 x 1,2x7,0x125	
	Rack	2 x 190,0x50,0	

1) without Lasertip

Kraftform XXL TX



12-piece screwdriver set for all-round applications

Code			
05051011001	● 160 i VDE	1 x 0,4x2,5x80 ¹⁾ ; 1 x 0,6x3,5x100	1
	● 247	1 x 0,5x3,0x70	
	● 335	1 x 0,8x4,0x100	
	⊕ 350 PH	1 x PH 2x100	
	⊕ 355 PZ	1 x PZ 1x80; 1 x PZ 2x100	
	⊕ 367 TORX®	1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100	
	● 932 A	1 x 1,0x5,5x100; 1 x 1,2x7,0x125	
	Rack	2 x 190,0x50,0	

1) without Lasertip

Kraftform Comfort

The Kraftform Comfort series offers a wide and diverse range of screwdrivers for universal use, with the distinctive Kraftform handle.



The multi-component Kraftform handle **for quick and low-exertion working.**



The screw symbol and tip size identification markings on the handle **make it easier to find** the right screwdriver in the tool case, or at the workplace.



The hexagonal non-roll feature **prevents any annoying rolling away.**



The Wera Black Point tip and a refined hardening process ensure **long service life of the tip, improved corrosion protection and an exact fit.**



The bit material used for manufacturing is subjected to a specific Wera hardening process, and this ensures **longer product service life.**

Kraftform Classic

Kraftform Classic also offers the distinctive Kraftform handle in a single-component variant.



Screwdrivers



The ergonomic Kraftform handle **prevents injury to the hand-arm system.**



The hexagonal non-roll feature **prevents any annoying rolling away** at the workplace.



The Wera Black Point tip and a refined hardening process ensure **long service life of the tip, improved corrosion protection and an exact fit.**



The bit material used for manufacturing is subjected to a specific Wera hardening process and this ensures **longer product service life.**



Kraftform Comfort

Convenient, safe, good!

1335 Screwdriver for slotted screws



Application: Slotted screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05031400001	0,4	2,0	60	81	2,5	5/64"	2 3/8"	10
05031401001	0,4	2,5	75	81	2,5	3/32"	3"	10
05031402001	0,5	3,0	80	81	3,0	1/8"	3 1/8"	10
05031403001	0,5	3,0	150	81	3,0	1/8"	6"	10
05031404001	0,5	3,0	200	81	3,0	1/8"	8"	5
05031405001	0,6	3,5	100	81	3,5	9/64"	4"	10
05031406001	0,6	3,5	125	81	3,5	9/64"	5"	10
05031407001	0,6	3,5	200	81	3,5	9/64"	8"	5
05031408001	0,8	4,0	100	98	4,0	5/32"	4"	10
05031409001	0,8	4,0	150	98	4,0	5/32"	6"	10
05031410001	0,8	4,0	200	98	4,0	5/32"	8"	5
05031411001	0,8	4,0	300	98	4,0	5/32"	12"	2
05031412001	1,0	5,5	125	98	5,5	7/32"	5"	10
05031413001	1,0	5,5	150	98	5,5	7/32"	6"	10
05031414001	1,0	5,5	200	98	5,5	7/32"	8"	5
05031415001	1,0	5,5	300	98	5,5	7/32"	12"	2
05031416001	1,2	6,0	100	105	6,0	15/64"	4"	10


1334 Screwdriver for slotted screws



Application: Slotted screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm
05031420001	0,8	5,0	100	98	3/16"	4"	10
05031421001	1,0	6,0	125	105	15/64"	5"	10
05031422001	1,2	6,5	150	105	1/4"	6"	10
05031423001	1,2	6,5	200	105	1/4"	8"	5
05031424001	1,2	7,0	150	105	9/32"	6"	10
05031425001	1,2	8,0	175	112	5/16"	7"	5
05031426001	1,6	8,0	175	112	5/16"	7"	5
05031427001	1,6	10,0	200	112	3/8"	8"	5


1334 SK Screwdriver for slotted screws



Application: Slotted screws
Blade: Hexagonal with bolster from 0.8 x 4.5
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	
05031430001	0,6	3,5	4	-	75	81	9/64"	3"	10
05031431001	0,8	4,0	4	-	90	81	5/32"	3 1/2"	10
05031432001	0,8	4,5	5	8	90	98	0,178"	3 1/2"	10
05031433001	1,0	5,5	6	10	100	98	7/32"	4"	10
05031434001	1,2	6,5	6	10	125	105	1/4"	5"	10
05031435001	1,2	7,0	6	10	125	112	9/32"	5"	10
05031436001	1,6	9,0	8	13	150	112	11/32"	6"	10
05031437001	1,6	10,0	8	13	175	112	3/8"	7"	5

1350 PH Screwdriver for Phillips screws




Application: Phillips screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	
05031440001	PH 0	60	81	3,0	2 3/8"	5
05031441001	PH 1	80	98	4,5	3 1/8"	10
05031442001	PH 1	200	98	4,5	8"	2
05031443001	PH 1	300	98	4,5	12"	2
05031444001	PH 2	100	105	6,0	4"	10
05031445001	PH 2	200	105	6,0	8"	2
05031446001	PH 2	300	105	6,0	12"	2
05031447001	PH 3	150	112	8,0	6"	5
05031448001	PH 4	200	112	10,0	8"	2




1350 SK PH Screwdriver for Phillips screws



Application: Phillips screws
Blade: Hexagonal, sizes 1 - 3 with bolster
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm		
05031450001	PH 0	4	60	81	2 3/8"	5	
05031451001	PH 1	5	8	80	98	2 3/8"	10
05031452001	PH 2	6	10	100	105	4"	10
05031453001	PH 3	8	13	150	112	4"	5

1355 PZ Screwdriver for Pozidriv screws



Application: Suitable for Pozidriv[®] screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	
05031460001	PZ 0	60	81	3,0	2 3/8"	10
05031461001	PZ 1	80	98	4,5	3 1/8"	10
05031462001	PZ 1	200	98	4,5	8"	2
05031463001	PZ 2	100	105	6,0	4"	10
05031464001	PZ 2	200	105	6,0	8"	2
05031465001	PZ 2	250	105	6,0	10"	2
05031466001	PZ 3	150	112	8,0	6"	5
05031467001	PZ 4	200	112	10,0	8"	2

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

1355 SK PZ Screwdriver for Pozidriv screws



Application: Suitable for Pozidriv[®] screws
Blade: Hexagonal, sizes 1-3 with bolster
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm		
05031470001	PZ 0	4	60	81	2 3/8"	5	
05031471001	PZ 1	5	8	80	98	3 1/8"	10
05031472001	PZ 2	6	10	100	105	4"	10
05031473001	PZ 3	8	13	150	112	6"	5

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

1367 TORX[®] screwdriver



Application: TORX[®] socket screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Comfort with non-roll feature, multi-component

Code	mm	mm	mm	mm	mm	
05031500001	TX 5	60	81	3,5	2 3/8"	10
05031501001	TX 6	60	81	3,5	2 3/8"	10
05031502001	TX 7	60	81	3,5	2 3/8"	10
05031503001	TX 8	60	81	3,5	2 3/8"	10
05031504001	TX 9	60	81	4,0	2 3/8"	10
05031505001	TX 10	80	81	4,0	3 1/8"	10
05031506001	TX 15	80	98	4,0	3 1/8"	10
05031507001	TX 20	100	98	4,5	4"	10
05031508001	TX 25	100	105	5,0	4"	10
05031509001	TX 27	115	105	5,5	4 9/16"	10
05031510001	TX 30	115	105	6,0	4 9/16"	10
05031511001	TX 40	130	112	7,0	5 3/16"	10
05031512001	TX 45	130	112	8,0	5 1/8"	10


TORX[®]

TORX[®] drive profiles transfer torque between tool and screw by line or surface contact rather than point contact as many other profiles. This protects both the screw and the tool profile. It also increases the amount of torque and power that can be transferred.

Kraftform Comfort

Convenient, safe, good!

1367 TORX® BO screwdriver



Application: TORX® socket screws with safety pin
(BO = with bore hole)

Blade: Round

Design: Chrome-plated, Black Point

Handle: Kraftform Comfort with non-roll feature, multi-component

Code						
Code		mm	mm	mm		
05031520001	TX 7	60	81	3,5	2 3/8"	5
05031521001	TX 8	60	81	3,5	2 3/8"	5
05031522001	TX 9	60	81	4,0	2 3/8"	5
05031523001	TX 10	80	81	4,0	3 1/8"	5
05031524001	TX 15	80	98	4,0	3 1/8"	5
05031525001	TX 20	100	98	4,5	4"	5
05031526001	TX 25	100	105	5,0	4"	5
05031527001	TX 27	115	105	5,5	4 9/16"	5
05031528001	TX 30	115	105	6,0	4 9/16"	5
05031529001	TX 40	130	112	7,0	5 1/8"	5

TORX® with borehole



TORX® tools with a borehole prevent the unauthorised unfastening of safety screws. The screws contain a pin that protrudes into the drive profile so that "normal" TORX® tools cannot be used. This pin fits into

the borehole of TORX® BO tools allowing safety screws to be unfastened.

1334/6 Screwdriver set Kraftform Comfort



Application: Slotted and Phillips screws

Content: 6-piece set in display carton

Code			
05031551001	● 1334	1 x 1,2x6,5x150	1
	● 1335	1 x 0,5x3,0x80; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	⊕ 1350 PH	1 x PH 1x80; 1 x PH 2x100	

1334 SK/6 Screwdriver set Kraftform Comfort



Hexagon



Application: Slotted and Phillips screws

Content: 6-piece set in display carton

Code			
05031556001	● 1334 SK	1 x 0,6x3,5x75; 1 x 0,8x4,0x90; 1 x 1,0x5,5x100; 1 x 1,2x6,5x125	1
	⊕ 1350 SK PH	1 x PH 1x80; 1 x PH 2x100	



1334/1355/6 Screwdriver set Kraftform Comfort



Application: Slotted and Pozidriv[®] screws

Content: 6-piece set in display carton

Code			
05031552001	1334	1 x 1,2x6,5x150	1
	1335	1 x 0,5x3,0x80; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	1355 PZ	1 x PZ 1x80; 1 x PZ 2x100	

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

1335/1350/1355/6 Screwdriver set Kraftform Comfort



Application: Slotted, Phillips and Pozidriv[®] screws

Content: 6-piece set in display carton

Code			
05031553001	1335	1 x 0,8x4,0x100; 1 x 1,0x5,5x125	1
	1350 PH	1 x PH 1x80; 1 x PH 2x100	
	1355 PZ	1 x PZ 1x80; 1 x PZ 2x100	

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

1334/1355 SK/6 Screwdriver set Kraftform Comfort



Hexagon

Application: Slotted and Pozidriv[®] screws

Content: 6-piece set in display carton

Code			
05031557001	1334 SK	1 x 0,6x3,5x75; 1 x 0,8x4,0x90; 1 x 1,0x5,5x100; 1 x 1,2x6,5x125	1
	1355 SK PZ	1 x PZ 1x80; 1 x PZ 2x100	

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

1367/6 TORX[®] screwdriver set Kraftform Comfort



Application: TORX[®] screws


Content: 6-piece set in display carton

Code			
05031554001	1367 TORX [®]	1 x TX 10x80; 1 x TX 15x80; 1 x TX 20x100; 1 x TX 25x100; 1 x TX 30x115; 1 x TX 40x130	1

Kraftform Classic

Proven quality over many years!


1735 Screwdriver for slotted screws



Application: Slotted screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Classic with non-roll feature, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05031209001	0,4	2,5	75	81	2,5	3/32"	3"	10
05031210001	0,5	3,0	80	81	3,0	9/64"	3 1/8"	10
05031211001	0,8	4,0	100	98	4,0	5/32"	4"	10
05031212001	1,0	5,5	125	98	5,5	7/32"	5"	10

1755 PZ Screwdriver for Pozidriv screws




Application: Suitable for Pozidriv® screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Classic with non-roll feature, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05031224001	PZ 0	60	81	3,0	2 3/8"			5
05031225001	PZ 1	80	98	4,5	3 1/8"			10
05031226001	PZ 2	100	105	6,0	4"			10
05031227001	PZ 3	150	112	8,0	6"			5

*) Pozidriv = reg. trademark of European Industrial Service Ltd.


1734 Screwdriver for slotted screws



Application: For slotted screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Classic with non-roll feature, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05031200001	1,2	6,5	150	105	6,0	1/4"	6"	10
05031201001	1,2	8,0	175	112	7,0	5/16"	7"	5
05031202001	1,6	10,0	200	112	9,0	3/8"	8"	5


1767 Screwdriver for TORX® screws



Application: TORX® socket screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Classic with non-roll feature, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05031300001	TX 8	60	81	3,5	2 3/8"			10
05031301001	TX 9	60	81	4,0	2 3/8"			10
05031302001	TX 10	80	81	4,0	3 1/8"			10
05031303001	TX 15	80	98	4,0	3 1/8"			10
05031304001	TX 20	100	98	4,5	4"			10
05031305001	TX 25	100	105	5,0	4"			10
05031306001	TX 30	115	105	6,0	4 9/16"			10
05031307001	TX 40	130	112	7,0	5 1/8"			10

1750 PH Screwdriver for Phillips screws



Application: Phillips screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform Classic with non-roll feature, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm
05031219001	PH 0	60	81	3,0	2 3/8"			5
05031220001	PH 1	80	98	4,5	3 1/8"			10
05031221001	PH 2	100	105	6,0	4"			10
05031222001	PH 3	150	112	8,0	6"			5



1734/6 Screwdriver set Kraftform Classic



Application: Slotted and Phillips screws

Content: 6-piece set in display carton

Code			
05031280001	1734	1 x 1,2x6,5x150	1
	1735	1 x 0,5x3,0x80; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	1750 PH	1 x PH 1x80; 1 x PH 2x100	

1734/55/6 Screwdriver set Kraftform Classic



Application: Slotted and Pozidriv[®] screws

Content: 6-piece set in display carton

Code			
05031281001	1734	1 x 1,2x6,5x150	1
	1735	1 x 0,5x3,0x80; 1 x 0,8x4,0x100; 1 x 1,0x5,5x125	
	1755 PZ	1 x PZ 1x80; 1 x PZ 2x100	

*) Pozidriv = reg. trademark of European Industrial Service Ltd.



How do I stop my screwdriver from rolling away?



Every Kraftform screwdriver has anti-roll protection at the lower end of the handle. The hexagonal shape stops screwdrivers from rolling away at the workplace.

Wooden Handle Series

The traditional screwdriver, with very specific product advantages and a robust beech wood handle.



The cylindrical handle is made of hard beech wood and ensures a **long product service life**, even when the tool is subject to high strain.



Higher torque can be transferred by fitting an open-jaw or ring spanner over the hex bolster that is welded to the blade.



A double leather cap combined with the blade that extends right through the handle provide **additional safety** and **reduce the danger of a splintering of the handle** when struck with a hammer.



The conventional screwdriver for traditionalists not wishing to make any compromises.

Wooden Handle Series

Traditional quality.

930 A Screwdriver for slotted screws



Application: Slotted screws
Blade: Round, hexagon bolster
Design: Chrome-plated, Black Point
Handle: Beech wood with leather cap

Code	mm	mm	mm	mm	mm	mm	mm	mm
05018005001	0,6	3,5	8	90	102	9/64"	3 1/2"	10
05018010001	0,8	4,5	8	90	102	0,178"	3 1/2"	10
05018015001	1,0	5,5	8	100	102	7/32"	4"	10
05018020001	1,2	7,0	10	125	111	9/32"	5"	10
05018025001	1,6	9,0	13	175	126	11/32"	7"	10
05018030001	1,6	10,0	13	175	126	3/8"	7"	5
05018035001	2,0	12,0	13	200	126	1/2"	8"	2
05018040001	2,5	14,0	16	250	140	9/16"	10"	2

935 SPH Screwdriver for Phillips screws



Application: Phillips screws
Blade: Round, hexagon bolster
Design: Chrome-plated, Black Point
Handle: Beech wood with leather cap

Code	mm	mm	mm	mm
05018350001	PH 1	8	90	102
05018352001	PH 2	10	100	111
05018354001	PH 3	13	175	126
05018355001	PH 4	16	200	140

955 SPZ Screwdriver for Pozidriv screws



Application: Suitable for Pozidriv[®] screws
Blade: Round, hexagon bolster
Design: Chrome-plated, Black Point
Handle: Beech wood with leather cap

Code	mm	mm	mm	mm
05023305001	PZ 1	8	90	102
05023307001	PZ 2	10	100	111
05023309001	PZ 3	13	175	126

^{*)} Pozidriv = reg. trademark of European Industrial Service Ltd.

930/935/6 Screwdriver set



Application: Slotted and Phillips screws
Content: 6-piece set in display carton

Code			
05018251001	930 A	1 x 0,6x3,5x90; 1 x 0,8x4,5x90; 1 x 1,0x5,5x100; 1 x 1,2x7,0x125	1
	935 SPH	1 x PH 1x90; 1 x PH 2x100	

930/955/6 Screwdriver set



Application: Slotted and Pozidriv[®] screws
Content: 6-piece set in display carton


Code			
05137810001	930 A	1 x 0,6x3,5x90; 1 x 0,8x4,5x90; 1 x 1,0x5,5x100; 1 x 1,2x7,0x125	1
	955 SPZ	1 x PZ 1x90; 1 x PZ 2x100	

^{*)} Pozidriv = reg. trademark of European Industrial Service Ltd.

Flagdriver and Stubby Series

The right tool for every application.

1267 A TORX® flagdriver



Application: TORX® socket screws
Blade: Round
Design: BlackLaser surface
Handle: Multi-component

Code			mm	mm	mm		
05026350001	TX 6		33	62,0	3,0	1 19/64"	10
05026351001	TX 7		33	62,0	3,0	1 19/64"	10
05026352001	TX 8		40	69,0	3,0	1 37/64"	10
05026353001	TX 9		40	69,0	3,0	1 37/64"	10
05026354001	TX 10		40	69,0	3,0	1 37/64"	10

1267 B TORX® combination flagdriver



Application: TORX® and hexagon socket screws
Blade: Hexagon
Design: TORX® and hexagon, BlackLaser surface
Handle: Multi-component

Code			mm	mm	mm		
05026370001	TX 9		3,5	42	81,0	1 5/8"	10
05026371001	TX 10		3,5	42	81,0	1 5/8"	10
05026372001	TX 15		3,5	47	86,0	1 27/32"	10
05026373001	TX 15		4	47	86,0	1 27/32"	10
05026374001	TX 20		4	47	86,0	1 27/32"	10

1267 A TORX PLUS® flagdriver



Application: TORX PLUS® socket screws
Blade: Round
Design: BlackLaser surface
Handle: Multi-component

Code			mm	mm	mm		
05026360001	6 IP		33	62,0	3,0	1 19/64"	10
05026361001	7 IP		33	62,0	3,0	1 19/64"	10
05026362001	8 IP		40	69,0	3,0	1 37/64"	10
05026363001	9 IP		40	69,0	3,0	1 37/64"	10
05026364001	10 IP		40	69,0	3,0	1 37/64"	10

1267 B TORX PLUS® combination flagdriver



Application: TORX PLUS® and hexagon socket screws
Blade: Hexagon
Design: TORX PLUS® and hexagon, BlackLaser surface
Handle: Multi-component

Code			mm	mm	mm		
05026380001	9 IP		3,5	42	81,0	1 5/8"	10
05026381001	10 IP		3,5	42	81,0	1 5/8"	10
05026382001	15 IP		3,5	47	86,0	1 27/32"	10
05026383001	15 IP		4	47	86,0	1 27/32"	10
05026384001	20 IP		4	47	86,0	1 27/32"	10



336 Stubby/Carburettor screwdriver



Application: Slotted screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform with non-roll feature, Weralit II, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05110068001	0,6	3,5	25	54	3,5	3/64"	1"	5	
05110069001	0,8	4,0	25	54	4,0	5/32"	1"	5	
05110070001	1,0	5,5	25	54	5,5	7/32"	1"	5	
05110075001	1,2	6,5	25	54	6,5	1/4"	1"	5	
05110078001	1,2	8,0	25	54	8,0	5/16"	1"	5	

Stubby/Carburettor screwdriver



Application: Suitable for Pozidriv[®] screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform with non-roll feature, Weralit II, single-component

Code		mm	mm	mm	mm	mm	mm	mm
05009330001	PZ 01	25	54	4,5	1"	5		
05009335001	PZ 02	25	54	6,0	1"	5		
05009337001	PZ 03	25	54	8,0	1"	5		

*) Pozidriv = reg. trademark of European Industrial Service Ltd.

337 Motorcycle screwdriver



Application: Slotted screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform with non-roll feature, Weralit II, single-component

Code	mm	mm	mm	mm	mm	mm	mm	mm	mm
05008507001	1,0	5,5	45	69	5,5	7/32"	1 3/4"	5	
05008509001	1,2	6,5	45	69	6,5	1/4"	1 3/4"	5	

Stubby/Carburettor screwdriver



Application: Phillips screws
Blade: Round
Design: Chrome-plated, Black Point
Handle: Kraftform, with non-roll feature, Weralit II, single-component

Code		mm	mm	mm	mm	mm
05008775001	PH 01	25	54	4,5	1"	5
05008780001	PH 02	25	54	6,0	1"	5
05008782001	PH 03	25	54	6,0	1"	5

Accessories

Indispensable aids for screwdrivers.

Wera Star - Magnetizer








		
Code	mm	
05073403001	48,0	1

1427 Awl



Handle: Weralit II, single-component

Blade: Extends through handle






				
Code	mm	mm		
05027405001	105	92	4 3/16"	5

1428 Reamer



Handle: Weralit II, single-component

Blade: Extends through handle

				
Code	mm	mm		
05027455001	107	92	4 9/32"	5



How to hold any screw securely on the screwdriver



The Wera magnetiser/demagnetiser: simply run the tool down the positive side of the Wera magnetiser/demagnetiser and the tool immediately becomes magnetised and is able to hold the screw securely on the blade. To demagnetise the tool, simply run it down one of the four negative sides.

335 MS Slotted screwdriver

NEW



Application: Suitable for less demanding screwdriving jobs and for general uses such as e.g. depth of profile measurements, checking for signs of rusting, removal of dirt

Blade: Round

Design: Stainless steel for high corrosion protection

Handle: Kraffform with non-roll feature, single-component, cellulose acetate, equipped with practical clip for attaching e. g. to the breast pocket

Code	mm	mm	mm	mm	mm	mm	mm	mm
05008004001	0,5	3,0	50	70	3,0	1/8"	2"	5

Rack for Kraffform screwdrivers



Code	mm	mm
05134001001	190,0	50,0

Rack for Kraffform Micro screwdrivers



Code	mm	mm
05134002001	190,0	80



Screwdrivers

Accessories

Indispensable aids for screwdrivers.

And this is how the gripper works:



Push the screw gripper onto the tip of the screwdriver until the end of the blade protrudes from the rubber blade holder.




Attach the screw to the tip of the blade and secure it in the screw gripper.



Pull the screw gripper towards the screwdriver handle until the two arms of the gripper sit against the head of the screw and are spread slightly apart. The Wera screw gripper releases the screw automatically after it has been fastened.




The two gripper arms spread further apart as they are pushed against the surface and automatically snap back when the head of the screw is countersunk.



When fastening screws in blind holes the screw gripper is pushed back, making it possible to reach even deep-seated screws.

1440/1442 Screw gripper set



NEW

Application: Attachment with holding function for screws, holds all screw profiles and sizes securely on the tool, suitable for round and hexagon blades with a diameter from 4.5 mm to 6.0 mm and 6.5 mm to 8.0 mm

Construction: Elastomer

Code			
05073680001	1440	1 x 4,5-6,0	1
	1442	1 x 6,5-8,0	

1441 Screw gripper attachment for screwdriver blades, long bits and L-keys with holding function for screws



NEW

Application: Attachment with holding function for screws, holds all screw profiles and sizes securely on the tool, suitable for round and hexagon blades with a diameter from 4.5 mm to 6.0 mm

Design: Elastomer

Code			
05073681001	1441	1 x 4,5-6,0	1

