

# L6360

# IO-Link communication master transceiver IC

Datasheet - production data



## Features

- Supply voltage from 18 V to 32.5 V
- Programmable output stages: high-side, lowside or push-pull (< 2 Ω)</li>
- Up to 500 mA L+ protected high-side driver
- COM1, COM2 and COM3 mode supported
- Additional IEC61131-2 type 1 input
- Short-circuit and overcurrent output protection through current limitation and programmable cut-off current
- 3.3 V / 5 V, 50 mA linear regulator
- 5 mA IO-Link digital input
- Fast mode I<sup>2</sup>C for IC control, configuration and diagnostic
- Diagnostic dual LED sequence generator and driver
- 5 V and 3.3 V compatible I/Os
- Overvoltage protection (> 36 V)
- Overtemperature protection
- ESD protection
- Miniaturized VFQFPN 26L (3.5x5x1 mm) package

# Applications

- Industrial sensors
- Factory automation
- Process control

# Description

The L6360 is a monolithic IO-Link master port compliant with PHY2 (3-wire) supporting COM1 (4.8 kbaud), COM2 (38.4 kbaud) and COM3 (230.4 kbaud) modes. The C/Qo output stage is programmable: high-side, low-side or push-pull; also cut-off current, cut-off current delay time, and restart delay are programmable. Cut-off current and cut-off current delay time, combined with thermal shutdown and automatic restart, protect the device against overload and shortcircuit. C/Qo and L+ output stages are able to drive resistive, inductive and capacitive loads. Inductive loads up to 10 mJ can be driven. Supply voltage is monitored and low voltage conditions are detected. The L6360 transfers, through the PHY2(C/Q<sub>0</sub> pin), data received from a host microcontroller through the USART (IN C/Q<sub>0</sub> pin), or to the USART (OUT C/Q<sub>1</sub> pin) data received from PHY2 (C/Q<sub>1</sub> pin). To enable full IC control, configuration and monitoring (i.e. fault conditions stored in the status register), the communication between the system microcontroller and the L6360 is based on a fast mode 2-wire I<sup>2</sup>C. The L6360 has nine registers to manage the programmable parameters and the status of the IC. Monitored fault conditions are: L+ line, overtemperature, C/Q overload, linear regulator undervoltage, and parity check. Internal LED driver circuitries, in open drain configuration, provide two programmable sequences to drive two LEDs.

November 2017

DocID022817 Rev 6

This is information on a product in full production.

1 6360	
LOSOU	

Cor	ntents		
1	Block di	agram	7
2		cription	
3	Absolute	e maximum ratings	10
4	Recomm	nended operating conditions	11
5		al characteristics	
6	Device c	configuration	19
	6.1	Introduction	
	6.2	Main features	19
	6.3	General description	19
	6.4	SDA/SCL line control	19
	6.5	Mode selection	19
	6.6	Functional description	
	6.7	Communication flow	21
	6.8	I <sup>2</sup> C address	
	6.9	Internal register	22
	6.10	Start-up default configuration	
	6.11	Interrupt	
	6.12	Demagnetization	
		<ul><li>6.12.1 Fast demagnetization</li><li>6.12.2 Slow demagnetization</li></ul>	
7	I <sup>2</sup> C proto	ocol	
1	7.1	Protocol configuration	
	7.1	Operating modes	
8		I layer communication	
U	8.1	Transceiver	
	8.2	IEC 61131-2 type 1 digital inputs	
9	-	tic LED sequence generator and driver	
10	-	ulator	
11	•	ion examples	
12		otection considerations	
12	12.1	Supply voltage protection	
	12.1	I/O line protection	
2/63	12.2	DocID022817 Rev 6	57

L6360			Contents
13	Package	information	59
	13.1	VFQFPN 26L (3.5x5x1 mm) package information	59
	13.2	VFQFPN 26L (3.5x5x1 mm) packing information	60

		Ordering information	
14	Revision	history	62



# List of tables

Table 1: Pin description	
Table 2: Absolute maximum ratings	10
Table 3: Recommended operating conditions	
Table 4: Thermal data	11
Table 5: Supply	
Table 6: Electrical characteristics - linear regulator	15
Table 7: Electrical characteristics - logic inputs and outputs	15
Table 8: Electrical characteristics - LED driving	15
Table 9: Electrical characteristics - I <sup>2</sup> C (fast mode)	15
Table 10: Main parameter typical variations vs. +/- 1% variation of Rbias value	17
Table 11: Register addresses	22
Table 12: ENCGQ: C/Q pull-down enable	25
Table 13: Icoq: C/QO HS and LS cut-off current	25
Table 14: tdcoq: C/QO HS and LS cut-off current delay time	25
Table 15: trcoq: C/QO restart delay time	26
Table 16: tdbq: C/QI debounce time	26
Table 17: ENCGI: I/Q pull-down enable	26
Table 18: CQPDG: C/Q pull-down generator switching	27
Table 19: L+COD: L+ cut-off disable	27
Table 20: tDCOL: L+ HS cut-off current delay time	27
Table 21: tRCOL: L+ restart delay	
Table 22: Bit 1:0 = tdbi [1:0]: I/Q debounce time	
Table 23: C/Q output stage configuration	28
Table 24: Parameter default configuration	32
Table 25: Register default configuration	
Table 26: Current write mode direction bit	40
Table 27: Sequential write mode direction bit	42
Table 28: Read mode: register address	43
Table 29: Address register	
Table 30: Linear regulator selection pin	
Table 31: Maximum CLOADon L+ for ILOAD= 400 mA	
Table 32: Supply voltage protection component description	
Table 33: Refined supply voltage protection component description	56
Table 34: VH protection component description	57
Table 35: Typical protection in IO-Link application component description	57
Table 36: IO-Link and SIO application extended protection component description	58
Table 37: VFQFPN 26L (3.5x5x1.0 mm) package mechanical data	60
Table 38: Ordering information	
Table 39: Document revision history	62



# List of figures

Figure 1: Block diagram Figure 2: Pin connection (top through view) Figure 3: Rise/fall time test setup	8 16
Figure 4: Normalized rise and fall time vs. output capacitor value (typ. values in push-pull configur	
Figure 5: A master transmitter addressing a slave receiver with a 7-bit address (the transfer is not changed)	
Figure 6: A master reads data from the slave immediately after the first byte	20
Figure 7: Transfer sequencing	
Figure 8: I2C communication	
Figure 9: Status register	22
Figure 10: Power-on bit behavior	23
Figure 11: Overtemperature (OVT) bit behavior	23
Figure 12: Cut-off behavior	24
Figure 13: Control register 1	25
Figure 14: Control register 2	
Figure 15: Configuration register	28
Figure 16: LED1 registers	
Figure 17: LED2 registers	
Figure 18: Parity register	
Figure 19: Power stage, Q2 is not present on L+ output	
Figure 20: Fast demagnetization principle schematic. Load connected to L	
Figure 21: Fast demagnetization waveform. Load connected to L	
Figure 22: Slow demagnetization block. Load connected to L-	36
Figure 23: Slow demagnetization waveform. Load connected to GND	
Figure 24: Device initialization	
Figure 25: Current write mode flow chart procedure	
Figure 26: Current write mode frames	
Figure 27: Sequential write mode flow chart procedure	41
Figure 28: Sequential write mode frames	
Figure 29: Microcontroller parity check calculus	
Figure 30: Register sequence in sequential write mode	
Figure 31: Current read mode flow chart procedure	
Figure 32: Current read mode frames Figure 33: Current read communication flow	
Figure 33: Current read communication now Figure 34: Sequential/random read mode	
Figure 35: Sequential/random read communication flow	40
Figure 36: Block diagram communication mode	40 18
Figure 37: System communication mode	
Figure 38: C/Q or L+ channel cut-off protection	
Figure 39: C/Q or L+ channel current limitation and cut-off protection with latched restart	
Figure 40: LED drivers	
Figure 41: Linear regulator	
Figure 42: Linear regulator principle schematic	
Figure 43: Principal connections	
Figure 44: Application example (I/Q not used): IO-LINK device supplied by L+ pin	
Figure 45: Application example (I/Q not used): IO-Link device supplied by single channel IPS	
Figure 46: Application example: IO-Link devices supplied by dual channel IPS	
Figure 47: Supply voltage protection with uni-directional Transil	
Figure 48: Refined supply voltage protection	
Figure 49: VH protection vs. VCC	
Figure 50: Typical protection in IO-Link applications	
Figure 51: IO-Link and SIO application extended protection	



List of figures	L6360
Figure 52: VFQFPN 26L (3.5x5x1.0 mm) package outline	59
Figure 53: VFQFPN 26L (3.5x5x1.0 mm) carrier tape outline	



# 1 Block diagram





Figure 1: Block diagram





### Table 1: Pin description

Number	Name	Function	Туре	
1	Vcc	IC power supply	Supply	
2	L-	L- line (IC ground)	Supply	
3	V <sub>H</sub>	Linear regulator supply voltage	Supply	
4	V <sub>DD</sub>	Linear regulator output voltage	Output	
5	SA1	Serial address 1	Input	
6	SA2	Serial address 2	Input	
7	R <sub>bias</sub>	External resistor for internal reference generation	Input	
8	SEL	Linear regulator 3.3 V/5 V voltage selection. Output is 5 V when SEL pin is pulled to GND	Input	
9	EN <sub>C/Q</sub>	C/Q output enable	Input	
10	IN <sub>C/Q</sub>	C/Q channel logic input	Input	
11	OUT <sub>C/Q</sub>	C/Q channel logic output	Output	
12	OUT <sub>I/Q</sub>	I/Q channel logic output	Output	
13	EN <sub>L+</sub>	L+ switch enable. When $EN_{L+}$ is high the switch is closed	Input	
14	IRQ	Interrupt request signal (open drain)	Output	
15	SCL	Serial clock line	Input	
16	SDA	Serial data line Input/		
17	RST	Reset - active low	Input	
18	SA0	Serial address 0	Input	
19	LED1	Status/diagnostic LED (open drain)	Output	



### L6360

### Pin description

Number	Name	Function	Туре
20	LED2	Status/diagnostic LED (open drain)	Output
21	L-	L- line (IC ground)	Supply
22	Vcc	IC power supply	Supply
23	L+	L+ line	Supply
24	I/Q	I/Q channel line	Input
25	C/Q <sub>I</sub>	Transceiver (C/Q channel) line	Input
26	C/Q <sub>O</sub>	Transceiver (C/Q channel) line	Output



# 3 Absolute maximum ratings

## Table 2: Absolute maximum ratings

Symbol	ol Parameter Value		Unit	
Vcc	Supply voltage	Vclamp		
V <sub>SEL</sub>	Linear regulator selection pin voltage	-0.3 to 4		
V <sub>DD</sub>	Linear regulator output voltage	5.5		
V <sub>H</sub>	Linear regulator input voltage	Vcc		
V <sub>SDA</sub> , V <sub>SCL</sub> , Vsa0, Vsa1, Vsa2	l <sup>2</sup> C voltage	-0.3 to V <sub>DD</sub> + 0.3		
VLED1,2	LED1,2 voltage	-0.3 to V <sub>DD</sub> + 0.3	V	
Vc/QI, VI/Q	C/Q <sub>I</sub> , I/Q voltage	-0.3 to V <sub>CC</sub> + 0.3		
Vrst	Reset voltage	-0.3 to V <sub>DD</sub> + 0.3		
VIRQ	IRQ voltage	-0.3 to V <sub>DD</sub> + 0.3		
V <sub>Rbias</sub>	External precision resistance voltage	-03 to 4		
Vesd	V <sub>ESD</sub> Electrostatic discharge (human body model) 2			
Iclamp	Current through $V_{CLAMP}$ in surge test (1 kV, 500 $\Omega$ ) condition	2	А	
Ic/qo, IL+	C/Q <sub>0</sub> , L+ current (continuous)	Internally limited	А	
IOUT <sub>C/Q</sub> , IOUT <sub>I/Q</sub>	OUT <sub>C/Q</sub> , OUT <sub>I/Q</sub> output current ±5		mA	
I <sub>SDA</sub>	I <sup>2</sup> C transmission data current (open-drain pin)	10	mA	
I <sub>RQ</sub>	Interrupt request signal current	2 <sup>(1)</sup>	А	
ILED1,2	LED1, 2 current	10	mA	
Eload	L+ demagnetization energy	_+ demagnetization energy 10		
Ртот	Power dissipation at $T_c$ = 25 °C	Internally limited	W	
P <sub>LR</sub>	LR Linear regulator power dissipation 200		mW	
TJ	Junction operating temperature	Internally limited	*0	
T <sub>STG</sub>	T <sub>STG</sub> Storage temperature range -55 to 150		°C	

### Notes:

<sup>(1)</sup>Peak value during fast transient test only.



# 4 Recommended operating conditions

### Table 3: Recommended operating conditions

Symbol	Parameter	Min.	Тур.	Max.	Unit
Vcc	Supply voltage	18		32.5	V
Vн	Linear regulator input voltage	7		Vcc	V
fscL	SCL clock frequency			400	kHz
R <sub>bias</sub>	Precision resistance	-0.1%	124	0.1%	kΩ
TJ	Junction temperature	-40		125	°C

#### Table 4: Thermal data

Symbol Parameter		Тур.	Unit
R <sub>thj-case</sub> Thermal resistance, junction-to-case		6	°C/W
R <sub>thj-amb</sub>	Thermal resistance, junction-to-ambient <sup>(1)</sup>	50	°C/W

#### Notes:

<sup>(1)</sup>Mounted on FR4 PCB with 2 signal Cu layers and 2 power Cu layers interconnected through vias.



(18 V < V\_{CC} < 30 V; -40 °C < T\_J < 125 °C; V\_{DD} = 5 V; unless otherwise specified).

Table 5: Supply

Currench al	Devenuetor	Table 5: Supply	Min	Turra	May	11
Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
VCLAMP	Voltage clamp	l = 5 mA	36			V
Vuv	Undervoltage on threshold		16	17	18	V
$V_{\text{UVH}}$	Undervoltage hysteresis		0.3	1		V
Vregln5h	Linear regulator undervoltage high threshold	SEL = L	4.3		4.7	
Vregln5l	Linear regulator undervoltage low threshold	SEL = L	3.6		4.2	v
Vreg5hys	Linear regulator undervoltage hysteresis	SEL = L	0.1			v
Vregln33h	Linear regulator undervoltage high threshold	SEL = H	2.8		3.1	
Vregln33l	Linear regulator undervoltage low threshold	SEL = H	2.5		2.7	V
Vreg33hys	Linear regulator undervoltage hysteresis	SEL = H	0.1			V
V <sub>QTHH</sub>	C/Q <sub>I</sub> and I/Q upper voltage threshold		10.5		12.9	V
Vqthl	C/Q <sub>I</sub> and I/Q lower voltage threshold		8		11.4	V
V <sub>QHY</sub>	C/Q and I/Q hysteresis voltage		1			V
V <sub>demag</sub>	L+ demagnetization voltage	I = 5 mA	-8.5	-6.5	-4.8	V
V <sub>fHS</sub>	C/Q high-side freewheeling diode forward voltage	I = 10 mA		0.5		V
V <sub>fLS</sub>	C/Q low-side freewheeling diode forward voltage	I = 10 mA		0.5		V
VLTHOFF	L+ line diagnostic lower threshold		9	10	11	V
VLTHY	L+ line diagnostic hysteresis		0.1	1		V
VLTHON	L+ line diagnostic upper threshold		10	11	12	V



	Electrical characteristics					
Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
	Cumply current	OFF-state		100		μA
ls	Supply current	ON-state Vcc at 32.5 V		4		mA
Ioffcq	OFF-state C/Q <sub>0</sub> current	$EN_{C/Q}=0,V_{C/Q}=0V$			1	μA
			70	115	190	
1	C/Q <sub>0</sub> low- and high-	Drogrammable	150	220	300	
Ιςοα	side cut-off current	Programmable	290	350	440	mA
		430	580	720		
ILIMQ	C/Q <sub>O</sub> low- and high- side limitation current		500		1600	mA
IOFFL	L+ OFF-state current	$EN_{L+} = 0, V_{L+} = 0 V$	0		200	μA
ICOL	L+ cut-off current		480	580	730	mA
ILIML	L+ limitation current		500		1600	mA
lucerec	C/Q <sub>I</sub> pull-down	Drogrommoble	5		6.5	mA
INC/Qi	current	Programmable	2		3.3	mA
Iini/q	I/Q pull-down current		2		3	mA
Baum	L+ high-side ON-	$I_{OUT} = 0.2 \text{ A at } T_J = 25 ^\circ\text{C}$		1		Ω
Ronl	state resistance	$I_{OUT} = 0.2 \text{ A at } T_J = 125 ^\circ\text{C}$			2	Ω
Roncah	C/Qo high-side ON-	$I_{OUT} = 0.2 \text{ A at } T_J = 25 ^\circ\text{C}$		1		Ω
NONCQH	state resistance	$I_{OUT}$ = 0.2 A at $T_J$ = 125 °C			2	Ω
Roncal	C/Qo low-side ON-	$I_{OUT} = 0.2 \text{ A at } T_J = 25 ^\circ\text{C}$		0.6		Ω
RONCQL	state resistance	$I_{OUT} = 0.2 \text{ A at } T_J = 125 ^{\circ}\text{C}$			1.2	Ω
t	IN <sub>C/Q</sub> to C/Qo propagation delay	Push-pull (CQ <sub>o</sub> rising edge)		140		ns
t <sub>dINC/Q</sub>	time	Push-pull (CQ <sub>O</sub> falling edge)		160		ns
taura	EN <sub>C/Q</sub> to C/Qo propagation delay	Push-pull (CQ <sub>o</sub> rising edge)		110		ns
tenc/q	time	Push-pull (CQ <sub>O</sub> falling edge)		225		ns
trPP	C/Q rise time in push-pull configuration	10% to 90%	250		860	ns
t <sub>fPP</sub>	C/Q fall time in push-pull configuration	10% to 90%	290		860	ns
tr∺s	C/Q rise time in high-side configuration			410		ns
t <sub>fHS</sub>	C/Q fall time in high-side configuration			700		ns



Symbol	Parameter	Test conditions	Min.	Typ	Max.	Unit
Symbol		Test conditions	wiin.	Тур.	wax.	Unit
trLS	C/Q rise time in low-side configuration			750		ns
t <sub>fLS</sub>	C/Q fall time in low- side configuration			530		ns
tenl	ENL to L+ propagation delay time			1		μs
t <sub>rL+</sub>	L+ rise time			3		μs
t <sub>fL+</sub>	L+ fall time			25		μs
4	C/Q <sub>I</sub> to OUT <sub>C/Q</sub> (falling) propagation delay time			40		ns
t <sub>dC/Qi</sub>	C/Q <sub>I</sub> to OUT <sub>C/Q</sub> (rising) propagation delay time			100		ns
tura	I/Q to OUT <sub>I/Q</sub> (falling) propagation delay time			40		ns
t <sub>dl/Q</sub>	I/Q to OUT <sub>I/Q</sub> (rising) propagation delay time			100		ns
				100		μs
	C/Qo low- and high-	Des manuelle		150		μs
t <sub>dcoq</sub>	side cut-off current delay time	Programmable		200		μs
				250		μs
	C/Qo restart delay			255 × t <sub>dcoq</sub>		
t <sub>rcoq</sub>	time	Programmable		Latched <sup>(1)</sup>		μs
				0		
		5		5		
tdbq	C/Q <sub>1</sub> debounce time	Programmable		20		μs
				100		
				0		
		<b>_</b>		5	1	
t <sub>dbl</sub>	I/Q debounce time	Programmable		20	1	μs
				100	1	
	L+ cut-off current	_		500		
t <sub>dcol</sub>	delay time	Programmable		0	1	μs
	L+ restart delay	_		64		ms
t <sub>rcol</sub>	time	Programmable		Latched (1)		
Tjsd	Junction temperature shutdown			150		°C



Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
Тјнуѕт	Junction temperature thermal hysteresis			20		°C
T <sub>JRST</sub>	Junction temperature restart threshold			130		°C

### Notes:

<sup>(1)</sup>Unlatch through I<sup>2</sup>C communication.

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit	
M		SEL = L	4.84	5	5.13	V	
Vdd	Linear regulator output voltage	SEL = H	3.22	3.3	3.37	V	
I <sub>LIMR</sub>	Linear regulator output current limitation		65			mA	

#### Table 6: Electrical characteristics - linear regulator

#### Table 7: Electrical characteristics - logic inputs and outputs

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
VIL	Input low-level voltage				0.8	V
VIH	Input high-level voltage		2.2			V
VIHIS	Input hysteresis voltage			0.2		V
l <sub>IN</sub>	Input current	$V_{IN} = 5 V$			1	μA
Vol	Output low-level voltage	I <sub>OUT</sub> = -2 mA			0.5	V
Vон	Output high-level voltage	I <sub>OUT</sub> = 2 mA	V <sub>DD</sub> - 0.5 V			V
V <sub>LIRQ</sub>	Open drain output low-level voltage	Iout = 2 mA			0.5	V

### Table 8: Electrical characteristics - LED driving

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
VLED1,2	Open drain output low-level voltage	$I_{LED} = 2 \text{ mA}$			0.5	V
ILED	LED1, 2 leakage current	$V_{\text{LED1}} = V_{\text{LED2}} = 5 \text{ V}$		3		nA

### Table 9: Electrical characteristics - I<sup>2</sup>C (fast mode)

Symbol	Parameter	Test conditions	Min.	Max.	Unit
VIL(SDA)	SDA high level input voltage			0.3	V
VIH(SDA)	SDA high level input voltage		0.7 x V <sub>DD</sub>		V
VIL(SCL)	SCL low level input voltage			0.3	V
VIH(SCL)	SCL high level input voltage		0.7 x V <sub>DD</sub>		V




Symbol	Parameter	Test conditions	Min.	Max.	Unit
l <sub>IN</sub>	I <sup>2</sup> C SDA, SCL input current	(0.1 x V <sub>DD</sub> ) <v<sub>IN &lt; (0.9 x V<sub>DD</sub>)</v<sub>	-10	10	μA
t <sub>r(SDA)</sub>	I <sup>2</sup> C SDA rise time		20 + 0.1 C <sub>b</sub>	300	ns
tr(SCL)	I <sup>2</sup> C SCL rise time		20 + 0.1 C <sub>b</sub>	300	ns
t <sub>f(SDA)</sub>	I <sup>2</sup> SDA fall time		20 + 0.1 C <sub>b</sub>	300	ns
t <sub>f(SCL)</sub>	I <sup>2</sup> C SCL fall time		20 + 0.1 C <sub>b</sub>	300	ns
t <sub>su(SDA)</sub>	SDA set-up time		100		ns
<b>t</b> h(SDA)	SDA hold time			0.9	μs
t <sub>su(STA)</sub>	Repeated start condition setup		0.6		μs
$t_{\text{su}(\text{STO})}$	Top condition set-up time		0.6		μs
$t_{w(START/STOP)}$	Stop to start condition time (bus free)		1.3		μs
t <sub>w(SCLL)</sub>	SCL clock low time		1.3		μs
tw(SCLH)	SCL clock high time		0.6		μs
Cb	Capacitance for each bus line			400	pF
Cı	Capacitance for each I/O pin			10	pF




Values based on standard I<sup>2</sup>C protocol requirement.

Figure 3: Rise/fall time test setup







# Figure 4: Normalized rise and fall time vs. output capacitor value (typ. values in push-pull configuration)

		Typ. va	riation	vs. R <sub>bias</sub>
Symbol	Parameter	R	bias <b>[k</b>	2]
		122.74	124	125.24
ls	Supply current	0.76%	0	-0.50%
I <sub>INC/Qi</sub>	Input current C/Q <sub>i</sub> pin (5.5 mA)	0.93%	0	-0.93%
I <sub>INC/Qi</sub>	Input current C/Q <sub>i</sub> pin (2.5 mA)	0.75%	0	-1.13%
I <sub>INI/Q</sub>	Input current I/Q pin (2.5 mA)	0.85%	0	-0.85%
t <sub>dcoq</sub>	$C/Q_O$ low- and high-side cut-off current delay time	-2.44%	0	2.00%
Ιςοα	C/Qo low- and high-side cut-off current (115 mA)	1.19%	0	-1.28%
t <sub>dcol</sub>	L+ cut-off current delay time (500 µs)	-0.95%	0	0.47%
ICOL	L+ cut-off current	1.36%	0	-0.91%
t <sub>rcol</sub>	L+ restart delay time	-0.93%	0	0.97%
Vuv	Undervoltage ON-threshold	0.00%	0	0.00%
V <sub>DD</sub>	Linear regulator output voltage (3.3 V)	-0.03%	0	0.03%
Vdd	Linear regulator output voltage (5 V)	-0.02%	0	0.02%
ILIMQ	C/Q <sub>0</sub> high-side limitation current	0.64%	0	-0.71%
ILIMQ	C/Q <sub>0</sub> low-side limitation current	0.28%	0	-1.47%
I <sub>LIML</sub>	L+ limitation current	0.47%	0	-2.09%
Vqthh	C/Q <sub>I</sub> and I/Q upper voltage threshold	0.00%	0	0.00%
V <sub>QTHL</sub>	C/Q <sub>I</sub> and I/Q lower voltage threshold	0.00%	0	0.00%
Vqhy	C/Q and I/Q hysteresis voltage	0.00%	0	0.00%

### Table 10: Main parameter typical variations vs. +/- 1% variation of Rbias value



aracteris	tics			L6360
Symbol	Parameter	Typ. var	iation <sub>bias</sub> [kg	
Symbol	Falameter	122.74	124	125.24
t <sub>rPP</sub>	C/Q rise time in push-pull configuration	-1.59%	0	1.18%
t <sub>fPP</sub>	C/Q fall time in push-pull configuration	-2.14%	0	0.94%
t <sub>dINC/Q</sub>	$IN_{C/Q}$ to $C/Q_O$ propagation delay time (rising)	-1.44%	0	0.75%
t <sub>dINC/Q</sub>	$IN_{C/Q}$ to $C/Q_O$ propagation delay time (falling)	-2.36%	0	0.18%
t <sub>dC/Qi</sub>	C/Q <sub>I</sub> to OUT <sub>C/Q</sub> propagation delay time (rising)	0.49%	0	1.13%
t <sub>dC/Qi</sub>	$C/Q_l$ to $OUT_{C/Q}$ propagation delay time (falling)	1.82%	0	0.03%
t <sub>dbq</sub>	C/Q <sub>I</sub> debounce time (100 µs)	-1.76%	0	1.50%
t <sub>dcoq</sub>	$C/Q_{\rm O}$ low- and high-side cut-off current delay time (200 $\mu s)$	-1.27%	0	2.00%
Ιςοα	C/Q <sub>0</sub> low-side cut-off current (220 mA)	0.39%	0	-1.56%
Ιςοα	C/Q <sub>0</sub> low-side cut-off current (350 mA)	0.36%	0	-1.43%
Icoq	C/Q <sub>0</sub> low-side cut-off current (580 mA)	0.65%	0	-1.72%
t <sub>rcoq</sub>	C/Q <sub>0</sub> restart delay time	-0.90%	0	0.97%
Ιςοα	C/Qo high-side cut-off current (220 mA)	0.84%	0	-0.84%
Ιςοα	C/Qo high-side cut-off current (350 mA)	1.38%	0	-0.69%
Icoq	$C/Q_0$ high-side cut-off current (580 mA)	1.08%	0	-1.08%



# 6 Device configuration

SDA and SCL configure the L6360 device through I<sup>2</sup>C.

# 6.1 Introduction

The I<sup>2</sup>C bus interface serves as an interface between the microcontroller and the serial I<sup>2</sup>C bus. It provides single master functions, and controls all I<sup>2</sup>C bus-specific sequencing, protocol and timing. It supports fast I<sup>2</sup>C mode (400 kHz).

## 6.2 Main features

- Parallel bus/I<sup>2</sup>C protocol converter
- Interrupt generation
- Fast I<sup>2</sup>C mode
- 7-bit addressing

# 6.3 General description

In addition to receiving and transmitting data, this interface converts it from serial to parallel format and vice versa. The interface is connected to the I<sup>2</sup>C bus by a data pin (SDA) and a clock pin (SCL).

# 6.4 SDA/SCL line control

SDA is a bi-directional line, SCL is the clock input. SDA should be connected to a positive supply voltage via a current-source or pull-up resistor. When the bus is free, both lines are HIGH. The output stages of the devices connected to the bus must have an open drain or open collector output to perform the wired AND function. Data on the I<sup>2</sup>C bus can be transferred to rates up to 400 Kbit/s in fast mode. The number of interfaces connected to the bus is limited by the bus capacitance. For a single master application, the master's SCL output can be a push-pull driver provided that there are no devices on the bus which would stretch the clock. Transmitter mode: the microcontroller interface holds the clock line low before transmission. Receiver mode: the microcontroller interface holds the clock line low after reception. When the I<sup>2</sup>C microcontroller cell is enabled, the SDA and SCL ports must be configured as floating inputs. In this case, the value of the external pull-up resistors used depends on the application. When the I<sup>2</sup>C microcontroller cell is disabled, the SDA and SCL ports revert to being standard I/O port pins. On the L6360, the SDA output is an open drain pin.

# 6.5 Mode selection


Possible data transfer formats are:


- The master transmitter transmits to the slave receiver. The transfer direction is not changed
- The slave receiver acknowledges each byte
- The master reads data from the slave immediately after the first byte (see Figure 6: "A master reads data from the slave immediately after the first byte"). At the moment of the first acknowledge, the master transmitter becomes a master receiver and the slave receiver becomes a slave transmitter


This first acknowledge is still generated by the slave. Subsequent acknowledges are generated by the master. The STOP condition is generated by the master which sends a not-acknowledge (A) just prior to the STOP condition.



Figure 5: A master transmitter addressing a slave receiver with a 7-bit address (the transfer is not changed)







On the microcontroller, the interface can operate in the two following modes:

- Master transmitter/receiver
- Idle mode (default state)

The microcontroller interface automatically switches from idle to master receiver after it detects a START condition and from master receiver to idle after it detects a STOP condition. On the L6360 the interface can operate in the two following modes:


- Slave transmitter/receiver
- Idle mode (default state)

The interface automatically switches from idle to slave transmitter after it detects a START condition and from slave transmitter to idle after it detects a STOP condition.

# 6.6 Functional description


By default, the I<sup>2</sup>C microcontroller interface operates in idle; to switch from default idle mode to master mode a START condition generation is needed. The transfer sequencing is shown in the picture below.





# 6.7 Communication flow

The communication is managed by the microcontroller that generates the clock signal. A serial data transfer always begins with a START condition and ends with a STOP condition. Data is transferred as 8-bit bytes, MSB first. The first byte following the START condition contains the address (7 bits). The 9<sup>th</sup> clock pulse follows the 8<sup>th</sup> clock cycle of a byte transfer, during which the receiver must send an acknowledge bit to the transmitter.



Each byte is followed by an acknowledgment bit as indicated by the A or A blocks in the sequence. A START condition immediately followed by a STOP condition (void message) is a prohibited format.

# 6.8 I<sup>2</sup>C address

Each I<sup>2</sup>C connected to the bus is addressable by a unique address. The I<sup>2</sup>C address is 7 bits long, and there is a simple master/slave relationship. The LSB of the L6360 address can be programmed by means of dedicated IC pins (SA0, SA1 and SA2, which can be hard wired to V<sub>DD</sub> or GND, or handled by  $\mu$ C outputs): the microcontroller can interface up to 8 L6360 ICs. The I<sup>2</sup>C inside the device has 5 pins:

- SDA: data
- SCL: clock



- SA0: LSB of the L6360 address
- SA1: bit 1 of the L6360 address
- SA2: bit 2 of the L6360 address

The I<sup>2</sup>C L6360 IC address is:

- Fixed part (4 MSBits): set to "1100"
- Programmable part (3 LSBits) by hardware: from "000 to 111" connecting SAx pins to GND or VDD

In the L6360 the SDA is an open drain pin.

## 6.9 Internal register

The L6360 has some internal registers to perform control, configuration, and diagnostic operations. These registers are listed below:

- Status register
- Configuration register
- Control register 1
- Control register 2
- LED1 register MSB
- LED1 register LSB
- LED2 register MSB
- LED2 register LSB
- Parity register

Each register is addressable as follows:


#### Table 11: Register addresses

Address	Register name
0000	Status register
0001	Configuration register
0010	Control register 1
0011	Control register 2
0100	LED1 MSB
0101	LED1 LSB
0110	LED2 MSB
0111	LED2 LSB
1000	Parity register

### Status register

Read only

Reset value: [0000000]





The status register stores diagnostic information. It can be read to check the status of the run-time of the device (faults, warning, transmission corrupted, etc.). When a fault condition occurs, a bit (corresponding to the fault condition) in the status register is set and an interrupt (via the IRQ pin) is generated. If there is no persistent fault condition, the status register is cleared after a successful current read.

Bit 7 = PO: Power-on (L+ line)

This bit indicates the status of L+ line voltage. If the voltage goes under the lower threshold ( $V_{LTHOFF}$ ) and  $EN_{L+}$  is high, the PO bit is set. It is reset after a successful current read if the L+ voltage has returned above the upper threshold  $V_{LTHON}$  and the read operation has begun after the bit has been set. When the PO bit is high, IRQ is generated. During  $EN_{L+}$  transition (from low-level to high-level) and during L+ line voltage transition, a fault condition is reported setting the PO bit and activating the IRQ pin. To reset the fault a successful current read is necessary.





Figure 10: Power-on bit behavior

Bit 6 = not used: always at zero

Bit 5 = OVT: overtemperature fault

This bit indicates the status of the IC internal temperature. If the temperature goes above the thermal shutdown threshold (T >  $T_{JSD}$ ) the OVT bit is set. It is reset after a successful current read if the temperature has returned below the thermal restart threshold ( $T_{JDS}$  -  $T_{JHIST}$ ) and the read operation has begun after the bit has been set. When OVT bit is high, the power outputs are disabled and IRQ is generated.





51

Bit 4 = CQOL: C/Q overload

This bit is set if a cut-off occurs on the C/Q channel. It is reset after a successful current read if the restart delay time ( $t_{rcoq}$ ) has elapsed or the protection is latched (bit  $t_{rcoq} = 1$ ). The read operation should begin after the CQOL bit has been set. When CQOL bit is high, IRQ is generated. When CQOL bit is high and the protection is latched (bit  $t_{rcoq} = 1$  in control register 1), the C/Q power output is disabled. See next figure.




Figure 12: Cut-off behavior

### Bit 3 = LOL: L+ overload

This bit is set if a cut-off occurs on the L+ driver. It is reset after a successful current read if the restart delay time ( $t_{rcol}$ ) has elapsed or the protection is latched (bit  $t_{rcol} = 1$  in control register 2). The read operation should begin after the LOL bit has been set. When LOL bit is high, IRQ is generated. When LOL bit is high and the protection is latched (bit  $t_{rcol} = 1$  in control register 2), the L+ power output is disabled. The behavior is the same as the C/Q driver (see *Figure 12: "Cut-off behavior"*).

Bit 2 = not used: always at zero

Bit 1 = REG LN: linear regulator undervoltage fault

This bit is set in case of undervoltage of the linear regulator output ( $V_{REGLNL}$ ). It is reset after a successful current read if the linear regulator output has returned to normal operation and the read operation has begun after the bit has been set. When REGLN bit is high, IRQ is generated.



Bit 0 = PE: parity check error


This flag is set if parity error occurs.

### **Control register 1**

Read/write

Reset value: [00100001]





The control register holds the parameters to control the L6360.

Bit 7 =  $EN_{CGQ}$ : C/Q<sub>1</sub> pull-down enable

Table 12:	ENCGQ: C	/Q pull-down	enable
			onabio

EN <sub>CGQ</sub>	Pull-down generator status		
0		Always OFF	
1	If $EN_{C/Q} = 0$	ON	
	If $EN_{C/Q} = 1$	OFF	

Bit 6:5 =  $I_{COQ}$  [1:0]: C/Q<sub>0</sub> HS and LS cut-off current

This bit is used to configure the cut-off current value on the C/Q channel, as shown in the table below.

I <sub>coq</sub> [1]	I <sub>coq</sub> [0]	Тур.
0	0	115 mA
0	1	220 mA
1	0	350 mA
1	1	580 mA

Bit 4:3 =  $t_{dcoq}$  [1:0]: C/Q<sub>0</sub> HS and LS cut-off current delay time

The channel output driver is turned off after a delay ( $t_{dcoq}$ ) programmable by means of these two bits.

Table 14: tdcoq: C/QO HS and LS cut-off current delay time

t <sub>dcoq</sub> [1]	t <sub>dcoq</sub> [0]	Тур.
0	0	100 µs
0	1	150 µs
1	0	200 µs
1	1	250 μs <sup>(1)</sup>



25/63

#### Notes:

<sup>(1)</sup>According to power dissipation at 2 kHz switching, C < 1  $\mu$ F and power dissipation 0.7 W.

#### Bit 2 = $t_{rcoq}$ : C/Q<sub>O</sub> restart delay time

After a cut-off event, the channel driver automatically restarts after a delay ( $t_{rcoq}$ ) programmable by means of this bit.

Table	15:	trcoa	C/QO	restart	delay	/ time
IUDIC		u coq.		i cotai t	acia	,

trcoq	Тур.
0	255x t <sub>dcoq</sub>
1	Latched <sup>(1)</sup>

#### Notes:

<sup>(1)</sup>Unlatch through I<sup>2</sup>C communication (reading or writing any internal register).

Bit 1:0 =  $t_{dbq}$  [1:0]: C/Q<sub>I</sub> debounce time

Debounce time is the minimum time that data must be in a given state after a transition. It is a programmable time, and can be configured as shown in the table below.


t <sub>dbq</sub> [1]	t <sub>dbq</sub> [0]	Тур.
0	0	0 µs
0	1	5 µs
1	0	20 µs
1	1	100 µs

### **Control register 2**

Read/write

Reset value: [0x100001]

#### Figure 14: Control register 2



The control register holds the parameters to control the L6360.

Bit 7 = EN<sub>CGI</sub>: I/Q pull-down enable

Table 17: ENCGI: I/Q pull-down enab	able 1	7: ENC	GI: I/Q r	oull-down	enable
-------------------------------------	--------	--------	-----------	-----------	--------

EN <sub>CGI</sub>	Pull-down generator status
0	Always OFF
1	Always ON

Bit 5 = CQ<sub>PDG</sub>: C/Q pull-down generator switching

In order to reduce consumption, it is possible to switch from default to low-power configuration by resetting the CQ<sub>PDG</sub> bit.

DocID022817 Rev 6	3
-------------------	---



	Table 18: CQPDG: C/Q pull-down generator switching				
CQPDG	Pull-down generator status				
0	I <sub>INI/Qi</sub> (input current C/Q <sub>i</sub> pin) = 2.5 mA				
1	$I_{INC/Qi}$ (input current C/Q <sub>i</sub> pin) = 5.5 mA				

### Bit $4 = L+_{COD}$ : L+ cut-off disable

1

The cut-off function on the L+ switch can be enabled or disabled according to the L+<sub>COD</sub> bit.

Table 19: L+COD: L+ cut-off disable		
L+cod	L+ cut-off current status	
0	Enabled	

As the cut-off function is intended to protect the integrated switches against overload and short-circuit, disabling the cut-off is not recommended.

Disabled

Bit  $3 = t_{DCOL}$ : L+ cut-off current delay time

The channel output driver is turned off after a delay (t<sub>DCOL</sub>) programmable by this bit.

Table 20: tDCOL: L+ HS cut-off	current delay time
	current delay time

tdcol	Тур.
0	500 µs
1	0 µs

Bit 2 =  $t_{RCOL}$ : L+ restart delay

After a cut-off event, the channel driver automatically restarts again after a delay ( $t_{RCOL}$ ) programmable by this bit.

trcol	Тур.
0	64 ms
1	Latched <sup>(1)</sup>

#### Notes:

<sup>(1)</sup>Unlatch through I<sup>2</sup>C communication (reading or writing any internal register).

#### Bit 1:0 = t<sub>dbi</sub> [1:0]: I/Q debounce time

Debounce time is the minimum time that data must be in a given state after a transition. It is a programmable time, and it can be configured as shown in the following table.



	Table 22: Bit 1:0 = tdbi [1:0]: I/Q debounce time						
t <sub>dbi</sub> [1]	t <sub>dbi</sub> [0]	Тур.					
0	0	0 µs					
0	1	5 µs					
1	0	20 µs					
1	1	100 µs					

### **Configuration register**

Read/write

Reset value: [100xxxxx]

### Figure 15: Configuration register



The configuration register holds data to configure the L6360 IC.

Bit 7:5 = C/Q[2:0]: C/Q output stage configuration

Table 23: C/Q o	utput stage configuration
Ormfinnentien	Nata

C/Q[2]	C/Q[1]	C/Q[0]	Configuration	Notes
0	0	0	OFF	HS and LS are OFF regardless of the state of $EN_{C/Q}$ and $IN_{C/Q}$ . The receiver is OFF regardless of the state of $EN_{C/Q}$ .
0	0	1	Low-side	HS is always disabled. LS is ON when IN <sub>C/Q</sub> is high and EN <sub>C/Q</sub> is high, OFF in all other cases. Slow asynchronous decay when the LS is turned off by EN <sub>C/Q</sub> or in case of cut-off. The receiver is OFF when EN <sub>C/Q</sub> is high: OUT <sub>C/Q</sub> is high. The receiver is ON when EN <sub>C/Q</sub> is low: if C/Q <sub>I</sub> is high, OUT <sub>C/Q</sub> is low. If C/Q <sub>I</sub> is low, OUT <sub>C/Q</sub> is high.
0	1	0	High-side	LS is always disabled. HS is ON when $IN_{C/Q}$ is low and $EN_{C/Q}$ is high, OFF in all other cases. Slow asynchronous decay if the HS is turned off by $EN_{C/Q}$ or in case of cut-off. The internal pull-down current generator on $C/Q_I$ should be disabled through control register 1, unless $C/Q_I$ is connected to $C/Q_O$ through a 100 $\Omega$ (or more) resistor. The receiver is OFF when $EN_{C/Q}$ is high: $OUT_{C/Q}$ is high. The receiver is ON when $EN_{C/Q}$ is low: if $C/Q_I$ is high, $OUT_{C/Q}$ is low. If $C/Q_I$ is low, $OUT_{C/Q}$ is high.



### L6360

## Device configuration

C/Q[2]	C/Q[1]	C/Q[0]	Configuration	Notes
				$IN_{C/Q}$ low and $EN_{C/Q}$ high: HS ON and LS OFF.
				$IN_{C/\!Q}$ high and $EN_{C/\!Q}$ high: LS ON and HS OFF.
0	1	1	Push-pull	If EN <sub>C/Q</sub> is low, both HS and LS are OFF. Slow asynchronous decay in case of cut-off or turn-off of both switches. An internal dead time is generated between each LS turn-off and the following HS turn-on and between each HS turn- off and the following LS turn-on.
				The receiver is OFF when $EN_{C/Q}$ is high: $OUT_{C/Q}$ is high.
				The receiver is ON when $EN_{C/Q}$ is low: if $C/Q_1$ is high, $OUT_{C/Q}$ is low. If $C/Q_1$ is low, $OUT_{C/Q}$ is high.
1	0	0	Tri-state	HS and LS are OFF regardless of the state of ENc/Q and INc/Q. The receiver is OFF when ENc/Q is high: OUT <sub>C</sub> /Q is high.
		Ū		The receiver is ON when $EN_{C/Q}$ is low: if $C/Q_1$ is high, $OUT_{C/Q}$ is low. If $C/Q_1$ is low, $OUT_{C/Q}$ is high.
				LS is ON regardless of the state of ENC/Q and INC/Q. Slow asynchronous decay in case of cut- off.
1	0	1	Low-side ON	The receiver is OFF when $\text{EN}_{\text{C/Q}}$ is high: $\text{OUT}_{\text{C/Q}}$ is high.
				The receiver is ON when EN <sub>C/Q</sub> is low: if C/Q <sub>I</sub> is high, OUT <sub>C/Q</sub> is low. If C/Q <sub>I</sub> is low, OUT <sub>C/Q</sub> is high.
				HS is ON regardless of the state of $EN_{C/Q}$ and $IN_{C/Q}$ . Slow asynchronous decay in case of cut- off.
1	1	0	High-side ON	The receiver is OFF when $\text{EN}_{\text{C/Q}}$ is high: $\text{OUT}_{\text{C/Q}}$ is high.
				The receiver is ON when $EN_{C/Q}$ is low: if $C/Q_I$ is high, $OUT_{C/Q}$ is low. If $C/Q_I$ is slow, $OUT_{C/Q}$ is high.



### **Device configuration**

C/Q[2]	C/Q[1]	C/Q[0]	Configuration	Notes
				IN <sub>C/Q</sub> low and EN <sub>C/Q</sub> high: HS ON and LS OFF. IN <sub>C/Q</sub> high and EN <sub>C/Q</sub> high: LS ON and HS OFF. If EN <sub>C/Q</sub> is low, both HS and LS are OFF.
1	1	1	Push-pull inductive load	Slow asynchronous decay in case of cut-off or turn-off of both switches. An internal dead time is generated between each LS turn-off and the following HS turn-on and between each HS turn- off and the following LS turn-on.
				The receiver is OFF when $EN_{C/Q}$ is high: $OUT_{C/Q}$ is high.
				The receiver is ON when $EN_{C/Q}$ is low: if $C/Q_I$ is high, $OUT_{C/Q}$ is low. If $C/Q_I$ is low, $OUT_{C/Q}$ is high.



See also the Section 6.12: "Demagnetization".

In order to reduce the risk of damage to the output stage (e.g. switching from push-pull inductive load to any transceiver configuration while an inductive load has some residual energy), the user must not switch between any of two "active" (low-side, high-side, push-pull, low-side ON, high-side ON, push-pull inductive load) configurations of the bridge. For example, if the microcontroller needs to switch from push-pull to high-side configuration, it needs to modify the configuration register twice:

First-step: switch from push-pull to OFF (or tri-state)

Second-step: switch from OFF (or tri-state) to high-side

If the microcontroller asks for a forbidden jump between configurations, the IC remains in the previous configuration and reports a parity error to the microcontroller. In case of sequential write, no parity error is generated if the microcontroller rewrites the configuration register with the previous value; if the operation, instead, requires a forbidden jump, all data are rejected also for other registers (and a parity error is raised).

The L+ switch is a high-side switch. HS is ON when  $EN_{L+}$  is high, otherwise it is OFF. Fast decay with active clamp (-V<sub>demag</sub>) is operated when the HS is turned off or in the case of cut-off.

Receiver I/Q is always ON.

Bit 4:2 = not used

Bit 1:0 = not used

LED registers

See Section 9: "Diagnostic LED sequence generator and driver".

These registers are used to configure the two LED drivers integrated in the IC. Each LED driver has two associated registers and turns on or off the external LED according to the information stored in the registers, which are scanned with a rate of 63 ms per bit. LED drivers can be used for status or diagnostic information, or for other purposes, and should be configured by the host microcontroller.



## LED1 registers Reset value: [00000000]

	Figure 16: LED1 registers							
15		14	13	12	11	10	9	8
L1R1	5	L1R <mark>14</mark>	L1R <mark>13</mark>	L1R <mark>12</mark>	L1R11	L1R <mark>10</mark>	L1R9	L1R8
7		6	5	4	3	2	1	0
L1R	7	L1R <mark>6</mark>	L1R5	L1R4	L1R3	L1R <mark>2</mark>	L1R1	L1R <mark>0</mark>

### LED2 registers

Reset value: [0000000]


Figure 17: LED2 registers							
15	14	13	12	11	10	9	8
L2R <mark>15</mark>	L2R14	L2R13	L2R12	L2R11	L2R10	L2R9	L2R <mark>8</mark>
7	6	5	4	3	2	1	0
L2R7	L2R6	L2R5	L2R4	L2R3	L2R2	L2R1	L2R0

Parity register

Read only

Reset value: [00000000]

Figure 18: Parity register



This register stores the parity of each register, calculated after the L6360 receives data registers.

Bit 7 = SR: status register parity

This bit is the parity of the status register.

Bit 6 = CR: configuration register parity

This bit is the parity of the configuration register.

Bit 5 = CT1: control register 1 parity

This bit is the parity of control register 1.

Bit 4 = CT2: control register 2 parity



This bit is the parity of control register 2.

Bit 3 = L1H: LED1 high register parity

This bit is the parity of the LED1 MSB register (15 down to 8).

Bit 2 = L1L: LED1 low register parity

This bit is the parity of the LED1.

LSB register (7 down to 0).

Bit 1 = L2H: LED2 high register parity

This bit is the parity of the LED2 MSB register (15 down to 8).

Bit 0 = L2L: LED2 low register parity

This bit is the parity of the LED2 LSB register (7 down to 0).

## 6.10 Start-up default configuration

Table 25: "Register default configuration" shows the device register default configuration.

#### Table 24: Parameter default configuration

Parameter	Default value
Icoq	220 mA
t <sub>dcoq</sub>	100 µs
trcoq	25 ms
t <sub>dbq</sub>	5 µs
t <sub>dcol</sub>	500 µs
t <sub>rcol</sub>	64 ms
t <sub>bdq</sub>	5 µs
Output stage	Tri-state

#### Table 25: Register default configuration

Registers	Bit position	Bit name	Reset value
	Bit 7	PO	0
	Bit 6	Not used	x
	Bit 5	OVT	0
Status register	Bit 4	CQOL	0
Status register	Bit 3	IQOL	0
	Bit 2	Not used	x
	Bit 1	REGLN	0
	Bit 0	PE	0
	Bit 7	C/Q2	1
Configuration register	Bit 6	C/Q1	0
	Bit 5	C/Q0	0
	Bit 4	Not used	x



### L6360

### Device configuration

_				
Registers	Bit position	Bit name	Reset value	
	Bit 3	Not used	x	
	Bit 2	Not used	x	
	Bit 1	Not used	x	
	Bit 0	Not used	x	
	Bit 7	ENcgq	0	
	Bit 6	I <sub>coq</sub> 1	0	
	Bit 5	I <sub>coq</sub> O	1	
Control register 1	Bit 4	t <sub>dcoq</sub> 1	0	
Control register 1	Bit 3	t <sub>dcoq</sub> 0	0	
	Bit 2	t <sub>rcoq</sub>	0	
	Bit 1	t <sub>dbq</sub> 1	0	
	Bit 0	t <sub>dbq</sub> 0	1	
	Bit 7	ENcgi	0	
	Bit 6	Not used	x	
	Bit 5	CQPDG	1	
	Bit 4	L+cod	0	
Control register 2	Bit 3	t <sub>dcoi</sub> 0	0	
	Bit 2	t <sub>rcoi</sub>	0	
	Bit 1	t <sub>dbi</sub> 1	0	
	Bit 0	t <sub>dbi</sub> 0	1	
	Bit 7	L1R15	0	
	Bit 6	L1R14	0	
	Bit 5	L1R13	0	
	Bit 4	L1R12	0	
LED1 register MSB	Bit 3	L1R11	0	
	Bit 2	L1R10	0	
	Bit 1	L1R9	0	
	Bit 0	L1R8	0	
	Bit 7	L1R7	0	
	Bit 6	L1R6	0	
	Bit 5	L1R5	0	
	Bit 4	L1R4	0	
LED1 register LSB	Bit 3	L1R3	0	
	Bit 2	L1R2	0	
	Bit 1	L1R1	0	
	Bit 0	L1R0	0	
LED2 register MSB	Bit 7	L2R15	0	
	1	1	I	



Device configuration L6360					
	Registers	Bit position	Bit name	Reset value	
		Bit 6	L2R14	0	
		Bit 5	L2R13	0	
		Bit 4	L2R12	0	
		Bit 3	L2R11	0	
		Bit 2	L2R10	0	
		Bit 1	L2R9	0	
		Bit 0	L2R8	0	
		Bit 7	L2R7	0	
		Bit 6	L2R6	0	
		Bit 5	L2R5	0	
		Bit 4	L2R4	0	
	LED2 register LSB	Bit 3	L2R3	0	
		Bit 2	L2R2	0	
		Bit 1	L2R1	0	
		Bit 0	L2R0	0	
	Derikaran	Bit 7	SR	0	
		Bit 6	CR	0	
		Bit 5	CT1	0	
		Bit 4	CT2	0	
	Parity register	Bit 3	L1H	0	
		Bit 2	L1L	0	
		Bit 1	L2H	0	
		Bit 0	L2L	0	

# 6.11 Interrupt


The IRQ pin (interrupt pin) should normally be held to a high logic level by an external pullup resistor or microcontroller pin configuration. The internal structure is an open drain transistor. It should be connected directly to the microcontroller so, in the case of a fault event (C/Q overload, power-on L+ line, overtemperature condition, etc.), it is pulled down to a low logic level, reporting the fault condition to the microcontroller.


# 6.12 Demagnetization

The power stage can be represented as shown in the following figure.



Figure 19: Power stage, Q2 is not present on L+ output





#### **Equation 1:**


#### $E = 1/2 LI^2$

This energy must be properly dissipated at the switch-off. Without an appropriate circuitry the output voltage would be pulled to very negative values, therefore recovering the stored energy through the breakdown of the power transistor. To avoid this, the output voltage must be clamped so that the voltage across the power switch does not exceed its breakdown voltage. In the case of load connected between the C/Q<sub>0</sub> pin and V<sub>cc</sub>, at switch-off (of the low-side switch) the output is pushed to a voltage higher than V<sub>cc</sub>.

### 6.12.1 Fast demagnetization

It applies to L+ channel only.







When a high-side driver turns off an inductance, a reversed polarity voltage appears across the load. The output pin (L+) of the power switch becomes more negative than the ground until it reaches the demagnetization voltage,  $V_{demag}$ . The conduction state of the power switch Q1 is linearly modulated by an internal circuitry in order to keep the voltage at C/Q



or I/Q pin at about  $V_{demag}$  until the energy in the load has been dissipated. The energy is dissipated in both IC internal switch and load resistance.






## 6.12.2 Slow demagnetization

It applies to C/Q channel.






When a high-side driver turns off an inductance a reversed polarity voltage appears across the load. In slow demagnetization configuration the low-side switch Q2 is ON and the C/Q pin is pulled to a voltage slightly (depending on Q2 drop) below the ground (L-). The energy is dissipated in both the IC internal switch and the load resistance. In the case of load connected between the C/Q pin and V<sub>CC</sub>, at switch-off (of the low-side switch Q2), the switch Q1 is ON and the output is pushed to a voltage slightly higher than V<sub>CC</sub>.




Device configuration





# 7 I<sup>2</sup>C protocol

## 7.1 Protocol configuration



Microcontroller initialization: microcontroller initialization phase.

Write mode: the L6360 is configured by the microcontroller through I<sup>2</sup>C. To configure the device, it is necessary to write its internal registers.

**Parity check:** the L6360 calculates the parity of each received register and stores it in the parity register. After which, it compares it with the parity transmitted together with the data. If the parity check of one or more registers failed, the "parity error bit" in the status register is set and an interrupt is generated by the L6360. The microcontroller can now read the status register and the parity register (current read). So the microcontroller can understand the interrupt cause and which register fails the transmission. If the parity check is ok, the flow goes on (read mode).

Write register failed: the microcontroller can again write the register(s) that failed the check.

Read mode: read status register to monitor if the configuration is good (read mode).

## 7.2 Operating modes

#### Writing modes

The L6360 is configured by the microcontroller through I<sup>2</sup>C. To configure the device, it is necessary to write its internal registers. There are two writing modes:


- Current: single register
- Sequential: all registers in sequence

#### Current write mode

The microcontroller I<sup>2</sup>C is configured as master transmitter. The L6360 I<sup>2</sup>C is configured as the slave receiver.








- 1. Microcontroller I<sup>2</sup>C establishes the communication: START condition.
- Microcontroller I<sup>2</sup>C sends the slave address on the I<sup>2</sup>C bus to check if the slave is online (1<sup>st</sup> frame).
- 3. After the address is matched, the microcontroller starts the data transmission: the 2<sup>nd</sup> frame is the data to be written into the selected register.
- 4. The 3<sup>rd</sup> frame is composed of the address of the register to be written and of the parity of the 2<sup>nd</sup> frame.
- 5. Microcontroller I<sup>2</sup>C finishes the communication: STOP condition.
- 6. The L6360 calculates the parity of the data received.
- 7. The L6360 compares its parity calculation with the parity bits in the 3<sup>rd</sup> frame (sent by the microcontroller).
- 8. If the parities match, the protocol flow goes on (exit), otherwise the PE bit inside the L6360 status register is set and the flow goes to the next state.
- 9. The L6360 generates an interrupt to report the parity check error.
- 10. The microcontroller sends a read request to the device. The L6360 then sends the status and parity registers. The microcontroller can resend the corrupted data register.
- 11. Back to step 1.

The I<sup>2</sup>C frame (configuration, control, diagnostic phases) must provide:

- Slave address (7 bits)
- Transmission direction (read/write)
- Data (8 bits: data register)
- Parity bits (P2, P1, P0)
- Register address (4 bits: 16 registers addressable)

The three frames are shown in the following figure:





#### 1<sup>st</sup> frame

Bit 7 to 1: the L6360 address

Bit 0: direction

#### Table 26: Current write mode direction bit

W bit	Master	Slave
0	Write mode	Read mode
1	Read mode	Write mode

### 2<sup>nd</sup> frame

Bit 7 to 0: data register

#### 3rd frame

Bit 7 to 5: parity bits

Bit 4: unused

Bit 3 to 0: register address

The parity check bits are calculated as shown in equation 2

#### **Equation 2:**

 $\mathsf{P0}=\mathsf{D7}\oplus\mathsf{D6}\oplus\mathsf{D5}\oplus\mathsf{D4}\oplus\mathsf{D3}\oplus\mathsf{D2}\oplus\mathsf{D1}\oplus\mathsf{D0}$ 

 $P1 = D7 \oplus D5 \oplus D3 \oplus D1$  (odd parity)

 $P2 = D6 \oplus D4 \oplus D2 \oplus D0$  (even parity)

Where  $\oplus$  means "XOR".


If parity error occurs, the register is not overwritten.

Sequential write mode





Figure 27: Sequential write mode flow chart procedure




- 1. The microcontroller I<sup>2</sup>C establishes the communication: START condition.
- 2. The microcontroller I<sup>2</sup>C sends the slave address on the I<sup>2</sup>C bus to check if the slave is online (1<sup>st</sup> frame).
- 3. After the address is matched, the microcontroller starts the sequential transmission (2<sup>nd</sup> to 8<sup>th</sup> frame).
- 4. The microcontroller sends its parity register (last frame: 9<sup>th</sup> frame).
- 5. Microcontroller I<sup>2</sup>C finishes the communication: STOP condition.
- 6. The L6360 calculates the parity of the registers received, and stores the results in the parity register.
- 7. The L6360 compares its parity register with the parity register sent by the microcontroller (9<sup>th</sup> frame).
- 8. If the parities match, the protocol flow goes on (EXIT), otherwise the PE bit inside the L6360 status register is set, and the flow goes to the next state.
- 9. The L6360 generates an interrupt to report the parity check error.
- 10. The microcontroller sends a read request to the device. In this phase the L6360 sends the status register and the parity register allowing the microcontroller to verify which register failed the configuration.
- 11. Now the microcontroller can perform a new write sequential procedure.
- 12. Microcontroller I<sup>2</sup>C establishes the communication: START condition.
- 13. Microcontroller I<sup>2</sup>C sends the slave address on the I<sup>2</sup>C bus to check if the slave is online.
- 14. The microcontroller resends the data registers.
- 15. Back to step 5.

The I<sup>2</sup>C frame (configuration, control, diagnostic phases) must provide:

- Slave address (7 bits)
- Transmission direction (read/write)
- Data (8 bits: data registers)

The 9 frames are shown below:





### 1<sup>st</sup> frame

Bit 7 to 1: the L6360 address

Bit 0: direction (write/read)

#### Table 27: Sequential write mode direction bit

W bit	Master	Slave
0	Write mode	Read mode
1	Read mode	Write mode

### 2<sup>nd</sup> to 8<sup>th</sup> frame

Bit 7 to 0: data register

## 9<sup>th</sup> frame

Bit 7 to 0: microcontroller parity register

The microcontroller parity check (for each register) calculus performed is shown below:

Figure 29: Microcontroller parity check calculus



Bit 6 = P6: microcontroller configuration register parity

This bit is the parity of the configuration register.

Bit 5 = P5: microcontroller control register 1 parity

This bit is the parity of control register 1.

Bit 4 = P4: microcontroller control register 2 parity

This bit is the parity of control register 2.

Bit 3 = P3: microcontroller LED1 register high parity



This bit is the parity of the LED1 MSB register (15 down to 8).

Bit 2 = P2: microcontroller LED1 register low parity

This bit is the parity of the LED1 LSB register (7 down to 0).

Bit 1 = P1: microcontroller LED2 register high parity

This bit is the parity of the LED2 MSB register high (15 down to 8).

Bit 0 = P0: microcontroller LED2 register low parity

This bit is the parity of the LED2 LSB register high (7 down to 0).

For each register, a parity check is calculated as shown in equation 3

#### Equation 3:

 $PX = D7 \oplus D6 \oplus D5 \oplus D4 \oplus D3 \oplus D2 \oplus D1 \oplus D0$  (X = 0 to 6)

D7 to D0 indicates bits inside each register.

Where  $\oplus$  means "XOR".

If parity error occurs, the registers are not overwritten.

In this writing mode, all writable registers and the microcontroller parity register are sent.

2 <sup>nd</sup> frame	0001	Configuration register	
3 <sup>rd</sup> frame	0010	Control register 1	
4 <sup>th</sup> frame	0011	Control register 2	
5 <sup>th</sup> frame	0100	LED1 register H	
6 <sup>th</sup> frame	0101	LED1 register L	
7 <sup>th</sup> frame		LED2 register H	
8 <sup>th</sup> frame		LED2 register L	
9 <sup>th</sup> frame		Microcontroller parity	

#### Figure 30: Register sequence in sequential write mode

#### **Read mode**

The status register and parity check register are read only. The other registers are readable/writable (by microcontroller). There are three reading modes:

- Current: status register only
- Sequential: all registers in sequence
- Random: to read registers in sequence starting from a register address fixed by the microcontroller

All registers are addressed as shown in the table below:


#### Table 28: Read mode: register address

Address	Register name
0000	Status register
0001	Configuration register
0010	Control register 1
0011	Control register 2
0100	LED1 register MSB



Address	Register name
0101	LED1 register LSB
0110	LED2 register MSB
0111	LED2 register LSB
1000	Parity register

#### **Current read mode**




- 1. Microcontroller I<sup>2</sup>C establishes the communication: START condition
- Microcontroller I<sup>2</sup>C sends slave address on the I<sup>2</sup>C bus to check if the slave is online (1<sup>st</sup> frame)
- 3. After the address is matched, the L6360 sends its status register (2<sup>nd</sup> frame)
- 4. The L6360 sends its parity register (3<sup>rd</sup> frame)
- 5. Microcontroller I<sup>2</sup>C finishes the communication: STOP condition

The I<sup>2</sup>C frame (configuration, control, diagnostic phases) must provide:


- Slave address (7 bits)
- Transmission direction (read/write)
- Data (8-bit data registers): status and parity registers

The three frames are shown in the following figure:






When a "read request" comes from the microcontroller (it is configured as master receiver), the IC (slave transmitter) sends the contents of the status and parity registers.



#### Sequential/random read modes



- 1. Random/sequential read mode initialization: microcontroller I<sup>2</sup>C establishes the communication: START condition.
- Microcontroller I<sup>2</sup>C sends the slave address, in write mode, on the I<sup>2</sup>C bus to check if the slave is online (1<sup>st</sup> frame).
- 3. Microcontroller I<sup>2</sup>C sends the register address start point, which sets the first register to read in sequence (2<sup>nd</sup> frame).
- 4. Microcontroller I<sup>2</sup>C finishes the communication: STOP condition.
- 5. Microcontroller I<sup>2</sup>C sends the slave address, in read mode, on the I<sup>2</sup>C bus to check if the slave is online (3<sup>rd</sup> frame).




- 6. After the address is matched, the L6360 sends its registers in sequential mode, starting from the register set in the 2<sup>nd</sup> frame.
- 7. The microcontroller I<sup>2</sup>C finishes the communication: STOP condition.

The I<sup>2</sup>C frame (configuration, control, diagnostic phases) must provide

- Slave address (7 bits)
- Transmission direction (read/write)
- Data (8-bit data register)

The frame structure is shown in the figure below

#### Figure 35: Sequential/random read communication flow



### 1<sup>st</sup> frame

Bit 7 to 1: the L6360 address

Bit 0: direction (write)

#### 2<sup>nd</sup> frame

Bit 7 to 0: address register starting point

#### Table 29: Address register

5	
Address	Register name
0000	Status register
0001	Configuration register
0010	Control register 1



Address	Register name
0011	Control register 2
0100	LED1 register MSB
0101	LED1 register LSB
0110	LED2 register MSB
0111	LED2 register LSB
1000	Parity register

## 3<sup>rd</sup> frame

Bit 7 to 1: L6360 address

Bit 0: direction (read)

### 4<sup>th</sup> to n<sup>th</sup> frame

Bit 7 to 0: data register (from address register starting point to penultimate address register)


9<sup>th</sup> frame


Bit 7 to 0: parity register (the last register)





# 8 Physical layer communication

The IC transfers the data received (on the  $IN_{C/Q}$  digital input pin) to the  $C/Q_0$  output. The  $EN_{C/Q}$  pin allows the  $C/Q_0$  line to be put into tri-state. Data received from the line ( $C/Q_1$  and I/Q pins) are transferred to the digital output pins  $OUT_{C/Q}$  and  $OUT_{I/Q}$ .











## 8.1 Transceiver

Output drivers (C/Q<sub>0</sub> and L+) are protected against short-circuit or overcurrent by means of two different functions. One is the current limiting function: output current is linearly limited to  $I_{LIMQ/L}$ . The cut-off protection, on the other side, turns off the drivers when the output current exceeds a (programmable for the C/Q<sub>0</sub> driver) threshold ( $I_{COL/I}$ ). When the current reaches the (programmed) cut-off value the channel output driver is turned off after a programmable delay ( $t_{dcoq/I}$ ). The channel output driver automatically restarts again after a programmable delay time ( $t_{rcoq/I}$ ).

L6360








## 8.2 IEC 61131-2 type 1 digital inputs

Two IEC61131-2 type 1 inputs are provided: one is available on C/Q<sub>I</sub> (as per IO-Link specification to support SIO mode) and one on I/Q pin. Both are provided with a programmable debounce filter ( $t_{dbq}$  and  $t_{dbi}$ , see *Table 17: "ENCGI: I/Q pull-down enable"* and *Table 23: "C/Q output stage configuration"*) to prevent false triggering.



# 9 Diagnostic LED sequence generator and driver

Each LED indication block can drive, through an open drain output, one external LED. LED drivers can be used for status or diagnostic information, or for other purposes, and should be configured by the host microcontroller. Two sequences of 16 bits can be programmed (through I<sup>2</sup>C) to generate user specific sequences; each LED driver has two associated registers and turns the external LED on or off according to the information stored in the registers, which are scanned at a rate of 63 ms per bit; total sequence time of each LED is approximately 1 s. Figure below shows how to wire up the two LEDs.







# 10 Line regulator

The L6360 embeds a linear regulator with output voltage selectable (by the SEL pin) at 3.3 V or 5 V.

The input voltage is  $V_{\rm H}$  and the maximum power dissipation is 200 mW. The linear regulator minimum limitation current value is  $I_{\rm LIMLR}.$ 




Figure 41: Linear regulator

Table 30: Linear regulator selection pin

SEL	VDD
0	5 V ± 2.5%
1	3.3 V ± 2%

The linear regulator cannot be turned off as it is necessary to supply (through VDD pin) internal circuitries. It can also be used to supply external circuitry (e.g. the microcontroller).





Figure 42: Linear regulator principle schematic




# 11 Application examples

The IO-Link master system typically consists of a microcontroller and physical layer and it communicates with an IO-Link device. The principle connection and the main application examples can be seen in the following figures.









In case of very high capacitive loads on L+ the IC could trigger the thermal protection threshold. The table below shows the maximum capacitance that L+ can supply without triggering the thermal protection.

Vcc [V]	Tamb[°C]	R <sub>LOAD</sub> [Ω]	CLOAD [µF]
24	25	220	
24	85	60	47
20	25	76	68
30	85	75	22

Table 31: Maximum CLOADon	L+ for ILOAD= 400 mA
---------------------------	----------------------

In case of very high capacitive loads the application schematic can be modified as reported in the following figures.



### Application examples

#### L6360





Figure 45: Application example (I/Q not used): IO-Link device supplied by single channel IPS

Figure 46: Application example: IO-Link devices supplied by dual channel IPS






# 12 EMC protection considerations

Depending on the final product use and environmental conditions, the master application may require additional protection.

## 12.1 Supply voltage protection

In order to avoid the overvoltage on a system supply, a voltage suppressor such as Transil™ can be added. A protection diagram example is shown in the figure below.

Figure 47: Supply voltage protection with uni-directional Transil




Performance of the above mentioned example is limited and does not include reverse polarity protection. It is just a cost-effective solution.

Part	Function	Description
D_S	Supply overvoltage protection	It works as a primary overvoltage clamp to limit supply line distortions, such as: surge pulses, oscillations caused by line parasitic parameters (inductance) during plug-in phase, etc. 1500 W is recommended to provide reliable protection, unidirectional type helps to avoid negative stress of the L6360.
C_F	Filtering bulk capacitor	An energy buffer for application supply filters the application supply to avoid high ripple during power driver switching.

#### Table 32: Supply voltage protection component description

A more sophisticated solution can be seen in the figure below.

### Figure 48: Refined supply voltage protection






Part	Function	Description
D_PWR	Primary overvoltage protection	It works as a primary overvoltage clamp to limit supply line distortions, such as: surge pulses, oscillations caused by line parasitic parameters (inductance) during plug-in phase. 1500 W is recommended to provide reliable protection, unidirectional type is chosen to cover reverse polarity protection.
D_POL	Reverse polarity protection	It avoids reverse direction current flow and negative voltage stress of the L6360. Its current rating (3 A) is chosen in accordance with the maximum driving capabilities of the L6360 power stages. Schottky type is recommended to limit power dissipation (low VF). Voltage rating (100 V) comes from negative surge to the supply condition.
D_S	D_PWR support and IO overvoltage protection	a) It shares a positive surge current with the primary protection and limits the overvoltage amplitude. b) It clamps surges applied to the L6360 C/Q and L+ lines.
C_F	Filtering bulk capacitor	An energy buffer for application supply filters the application supply to avoid high ripple during power driver switching etc.

Table 33: Refined supply voltage protection component description

If the  $V_H$  pin of the L6360 is supplied by a separate power supply or if it is decoupled by the main power supply and blocked by bulk capacitors, an additional circuit may be required to ensure the  $V_H$  voltage is always lower than (or equal to) the main supply voltage ( $V_{CC}$ ). A possible solution with diode is shown in the figure below.

Figure 49: VH protection vs. VCC






### EMC protection considerations

Table 34: VH protection component description			
Part	Function	Description	
D_VH	VH overvoltage protection	$V_{\rm H}$ voltage must be always lower than (or equal to) $V_{\rm CC}.$ Even during the powering-up and down of an application. This fact must be taken into consideration if $V_{\rm H}$ is supplied by another source ( $V_{\rm CC}$ and $V_{\rm H}$ not connected together), charged capacitors. In some cases a diode placed between $V_{\rm CC}$ and $V_{\rm H}$ may help to avoid this violation.	

Table 34: VH protection component description

## 12.2 I/O line protection

The figure below shows external components (capacitors) suitable for IO-Link communication, protection level in accordance with the specification.






Table 35: Typical protection in IO-Link application component description	Table 35: Typical	protection in	<b>IO-Link applic</b>	ation componen	t description
---	-------------------	---------------	-----------------------	----------------	---------------

Part	Function	Description	
C_1 Power supply locking		Energy buffer for the L6360 supply, makes chip supply voltage stable, limits EMI noise.	
C_I/Q, C_C/Q, C_L+	Filtration capacitors	Work as a basic protection against fast transient signals like burst or radio-frequency domain applied to the lines. Limit voltage spike frequency spectrum and amplitude.	

If an extended protection level is required, the solution seen in the next figure is recommended. It provides robust protection according to IEC61131-2. It is suitable for IO-Link communication and is backward compatible with SIO (standard I/O). It protects the L6360 application against high energy surge pulses according to the IEC61000-4-5 standard. All the lines are protected against ±2.5 kV surge pulse amplitude in common mode and ±1 kV in differential mode considering 42  $\Omega/0.5 \mu$ F generator coupling.








Table 36: IO-Link and SIO application extended protection component description

Part	Function	Description
C_I/Q, C_C/Q, C_L+	Filtration capacitors	Work as a basic protection against fast transient signals like burst or radio-frequency domain applied to the lines. Limit voltage spike frequency spectrum and amplitude.
D_I/Q, D_C/Q	Negative voltage spike suppression	Schottky diodes with low VF clamp the disturbance applied to the lines in a reverse polarity direction. Capable of conducting high surge current pulses to avoid high peak current flow through the L6360 pins
R_I/Q	Surge current limitation	Reduces the current flow in the L6360 - I/Q pin in both polarities when e.g. surge noise is applied to the line. If this resistor is omitted, I/Q line surge immunity is lower.
U2 (SPT01-335DEE)	Overvoltage protection	Primary surge protection to avoid overvoltage on the L6360 interface. Protects L+ switch against negative voltage pulses. Shares current flow of negative surge pulses with the additional Schottky diodes on C/Q and I/Q lines. Clamps positive surge pulse amplitude applied to I/Q line.




# 13 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK<sup>®</sup> packages, depending on their level of environmental compliance. ECOPACK<sup>®</sup> specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK<sup>®</sup> is an ST trademark.

# 13.1 VFQFPN 26L (3.5x5x1 mm) package information

Figure 52: VFQFPN 26L (3.5x5x1.0 mm) package outline







### Package information


Table 37: VFQFPN 26L (3.5x5x1.0 mm) package mechanical data				
Dim	mm			
Dim.	Min.	Тур.	Max.	
A	0.80	0.90	1.00	
A1	0.00	0.02	0.05	
A3		0.20		
b	0.18	0.25	0.30	
D	3.50 BSC			
D2	1.90	2.00	2.10	
E	5.00			
E2	3.40	3.50	3.60	
e		0.50		
L	0.30	0.40	0.50	
ddd		0.05		



VFQFPN stands for thermally enhanced very thin fine pitch quad flat package no lead. Very thin profile:  $0.80 < A \le 1.00$  mm. Details of terminal 1 are optional but must be located on the top surface of the package by using either a mold or marked features.

## 13.2 VFQFPN 26L (3.5x5x1 mm) packing information

Figure 53: VFQFPN 26L (3.5x5x1.0 mm) carrier tape outline





# 13.3 Ordering information

Table 38: Ordering information

Order code	Package	Packing
L6360TR	VFQFPN 26L (3.5x5x1 mm)	Tape and reel



# 14 Revision history

Table 39: Document revision history

Date	Revision	Changes	
12-Mar-2012	1	Initial release.	
15-Mar-2012	2	Updated E <sub>load</sub> definition in table 3: Absolute maximum ratings. Updated figure 36: Block diagram communication mode.	
25-Jan-2013	3	Updated table 4: Recommended operating conditions	
11-Mar-2016	4	Added figure titled "VFQFPN 26L (3.5x5x1.0 mm) carrier tape outline.	
10-May-2016	5	Updated Table 5: "Supply" and Table 24: "Parameter default configuration".	
		Updated Figure 2: "Pin connection (top through view)", Figure 15: "Configuration register", Figure 35: "Sequential/random read communication flow", Figure 36: "Block diagram communication mode", Figure 43: "Principal connections" and Figure 50: "Typical protection in IO-Link applications".	
20-Nov-2017	6	Added Figure 44: "Application example (I/Q not used): IO-LINK device supplied by L+ pin", Figure 45: "Application example (I/Q not used): IO-Link device supplied by single channel IPS", Figure 46: "Application example: IO-Link devices supplied by dual channel IPS" and Table 31: "Maximum CLOADon L+ for ILOAD= 400 mA".	
		Updated Table 1: "Pin description", Table 3: "Recommended operating conditions", Table 10: "Main parameter typical variations vs. +/- 1% variation of Rbias value".	



#### L6360

#### **IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics - All rights reserved

