


MDT1010C3IH-LVDS	1280 x 800	LVDS Interface	TFT Module
<b>Specification</b>			
Version: 1		Date: 18/05/2020	
<b>Revision</b>			
1	16/05/2020	First issue	

Display Features		
Display Size	10.10"	
Resolution	1280 x 800	
Orientation	Landscape	
Appearance	RGB	
Logic Voltage	3.3V	
Interface	LVDS	
Brightness	500 cd/m <sup>2</sup>	
Touchscreen	---	
Module Size	229.46 x 149.10 x 4.50 mm	
Operating Temperature	-20°C ~ +70°C	
Pinout	40 way connector	
Pitch	---	Weight / Display

\* - For full design functionality, please use this specification in conjunction with the EK79202 specification.(Provided Separately)

Display Accessories	
Part Number	Description

Optional Variants	
Appearances	Voltage



## General Specifications

	Feature	Spec
Characteristics	Size	10.1 inch
	Resolution	1280(Horizontal)*800(Vertical)
	Interface	LVDS
	Connect type	Connector
	Color Depth	16.7M
	Technology type	a-Si
	Display Spec. Pixel pitch (mm)	0.1695(H) $\times$ 0.1695(V)
	Pixel Configuration	R.G.B. Vertical Stripe
	Display Mode	Normally Black
	Driver IC	EK79202
	Viewing Direction	ALL
Mechanical	LCM (W x H x D) (mm)	229.46(W)*149.10(H)*4.5 (D)
	Active Area(mm)	216.96(H)x 135.60(V)
	With /Without TP	Without TP
	Weight (g)	TBD
	LED Numbers	45 LEDs

Note 1: Requirements on Environmental Protection: RoHS

Note 2: LCM weight tolerance: +/- 5%



## Input/Output Terminals

No.	Symbol	Description	Note
1	NC	No connection	
2-3	VDD (3.3V)	Power Supply	
4	NC	No connection	
5	RESET(NC)	No connection	
6	STBYB(NC)	No connection	
7	GND	Ground	
8	RXIN0-	- LVDS differential data input	
9	RXIN0+	+ LVDS differential data input	
10	GND	Ground	
11	RXIN1-	- LVDS differential data input	
12	RXIN1+	+ LVDS differential data input	
13	GND	Ground	
14	RXIN2-	- LVDS differential data input	
15	RXIN2+	+ LVDS differential data input	
16	GND	Ground	
17	RXCLK-	- LVDS differential clock input	
18	RXCLK+	+ LVDS differential clock input	
19	GND	Ground	
20	RXIN3-	- LVDS differential data input	
21	RXIN3+	+ LVDS differential data input	
22	GND	Ground	
23	SDA(NC)	No connection	
24	SCL(NC)	No connection	
25	GND	Ground	
26	CS(NC)	No connection	
27	NC	No connection	
28	LVBIT(NC)	No connection	
29	NC	No connection	
30	GND	Ground	
31-32	LEDK	Power for LED backlight (Cathode)	
33-38	NC	No connection	
39-40	LEDA	Power for LED backlight (Anode)	



## Absolute Maximum Ratings



Item	Symbol	MIN	Typ	MAX	Unit
Supply Voltage	VDD	-0.3	3.3	3.6	V
Input voltage "H" level	VIH	0.7VDD	-	VDD	V
Input voltage "L" level	VIL	0	-	0.3VDD	V
Operating Temperature	TOPR	-20	-	70	°C
Storage Temperature	TSTG	-30	-	80	°C

MIDAS  
design • manufacture • supply



# Electrical Characteristics

## POWER ON/OFF SEQUENCE




## Driving Backlight

Item	Symbol	MIN	TYP	MAX	Unit	Remark
Forward Current	$I_F$	-	270	-	mA	
Forward Voltage	$V_F$	14	16	18	V	
Backlight Power consumption	$W_{BL}$	-	4.32	-	W	
LED Lifetime		-	50000	-	Hrs	

Note 1: Each LED:  $I_F = 40 \text{ mA}$ ,  $V_F = 3.2 \pm 0.2 \text{ V}$ .

Note 2: Optical performance should be evaluated at  $T_a = 25^\circ \text{C}$  only.

Note 3: If LED is driven by high current, high ambient temperature & humidity condition. The life Time of LED will be reduced. Operating life means brightness goes down to 50% initial brightness. Typical operating life time is estimated data.



CIRCUIT DIAGRAM

design • manufacture • supply

## RESET TIMING CHARACTERISTICS

When RESETB of the reset pin equals to Low, it will be in the condition of reset. When it is in the condition of reset, it will make the device recover the initial set.

However, in order to avoid the reset noise cause reset, there is a mechanism to judge about whether the reset is needed or not.

The closed interval of Low can be shown as the following.

(Test condition:  $V_{DDIO} = 2.3 \text{ V} \sim 3.6 \text{ V}$ ,  $V_{SS} = 0 \text{ V}$ ,  $T_A = -20 \sim +85$ )


Parameter	Symbol	Conditions	Spec.			Unit
			Min.	Typ.	Max	
Reset low pulse width	$T_{rst}$		20	-	-	$\mu\text{s}$




Figure 13.5: Reset timing



## LVDS interface CHARACTERISTICS




6-bit LVDS input (LVBIT=L, LVFMT=Don't care)



8-bit LVDS input (LVBIT=H, LVFMT=L)





8-bit LVDS input(LVBIT=H, LVFMT=H)

For 1280RGBx800

Parameter	Symbol	Value			Unit
		Min.	Typ.	Max.	
DCLK frequency @Frame rate=60Hz (LVDS)	$F_{DCLK}$	66.3	72.4	78.9	MHz
HSYNC period time	$T_H$	1380	1440	1500	DCLK
Horizontal display area	$T_{HD}$	1280			DCLK
HSYNC pulse width	$T_{HPW}$	Min.	1		
		Typ.	-		
		Max.	40		
HSYNC back porch(with pulse width)	$T_{HBP}$	88	88	88	DCLK
HSYNC front porch	$T_{HFP}$	12	72	132	DCLK
VSYNC period time	$T_V$	824	838	872	H
Vertical display area	$T_{VD}$	800			H
VSYNC pulse width	$T_{VPW}$	Min.	1		H
		Typ.	-		
		Max.	20		
VSYNC back porch(with pulse width)	$T_{VBP}$	23	23	23	H
VSYNC front porch	$T_{VFP}$	1	15	49	H





## Optical Characteristics

Items		Symbol	Condition	Min.	Typ.	Max.	Unit	Remark
Viewing angles		$\theta_T$	Center CR $\geq$ 10		80	-	Degree.	Note2
		$\theta_B$			80	-		
		$\theta_L$			80	-		
		$\theta_R$			80	-		
Contrast Ratio		CR	$\theta = 0$	800	1000	-	-	Note1, Note3
Response Time		$T_{ON}$	25°C	-	25	35	ms	Note1, Note4
		$T_{OFF}$						
Chromaticity	White	$X_W$	Backlight is on	-	0.322	-	-	Note1, Note5
		$Y_W$		-	0.344	-	-	
Color Gamut		U		45	50	-	%	Note1, Note6
Luminance Uniformity		U		70	75	-	%	Note1, Note6
Luminance		L		450	500		cd/m <sup>2</sup>	Note1, Note7


Test Conditions:

1. IF= 20mA(one channel),the ambient temperature is 25°C.
2. The test systems refer to Note 1 and Note 2.

Note 1:Definition of optical measurement system.

The optical characteristics should be measured in dark room. After 5 minutes operation, the optical properties are measured at the center point of the LCD screen. All input terminals LCD panel must be ground when measuring the center area of the panel.





Note 2: Definition of viewing angle range and measurement system. viewing angle is measured at the center point of the LCD by CONOSCOPE(ergo-80).




Fig. 1 Definition of viewing angle

Note 3: Definition of contrast ratio

$$\text{Contrast ratio (CR)} = \frac{\text{Luminance measured when LCD is on the "White" state}}{\text{Luminance measured when LCD is on the "Black" state}}$$




“White state “:The state is that the LCD should driven by  $V_{white}$ .

“Black state”: The state is that the LCD should driven by  $V_{black}$ .

$V_{white}$ : To be determined     $V_{black}$ : To be determined.

Note 4: Definition of Response time

The response time is defined as the LCD optical switching time interval between “White” state and “Black” state. Rise time ( $T_{ON}$ ) is the time between photo detector output intensity changed from 90% to 10%. And fall time ( $T_{OFF}$ ) is the time between photo detector output intensity changed from 10% to 90%.



design • manufacture • supply

Note 5: Definition of color chromaticity (CIE1931)

Color coordinates measured at center point of LCD.

Note 6: Definition of Luminance Uniformity

Active area is divided into 9 measuring areas (Refer Fig. 2). Every measuring point is placed at the center of each measuring area.

$$\text{Luminance Uniformity}(U) = L_{min} / L_{max} \times 100\%$$

L——Active area length W—— Active area width






Fig. 2 Definition of uniformity

$L_{max}$ : The measured maximum luminance of all measurement position.

$L_{min}$ : The measured minimum luminance of all measurement position.

Note 7: Definition of Luminance : design • manufacture • supply

Measure the luminance of white state at center point.



## Environmental / Reliability Tests


No	Test Item	Condition	Remarks
1	High Temperature Opeartion	T <sub>s</sub> = +70°C, 96hrs	Note 1 IEC60068-2-2, GB2423. 2-89
2	Low Temperature Opeartion	T <sub>a</sub> = -20°C, 96hrs	Note 2 IEC60068-2-1 GB2423.1-89
3	High Temperature Storage	T <sub>a</sub> = +80°C, 96hrs	IEC60068-2-2 GB2423. 2-89
4	Low Temperature Storage	T <sub>a</sub> = -30°C, 96hrs	IEC60068-2-1 GB/T2423.1-89
5	High Temperature & Humidity Storage	T <sub>a</sub> = +60°C, 90% RH max, 96 hours	IEC60068-2-3 GB/T2423.3-2006
6	Thermal Shock (Non-operation)	-30°C 30 min ~ +80°C 30 min Change time: 5min, 30 Cycle	Start with cold temperature, end with high temperature IEC60068-2-14, GB2423.22-87
7	Electro Static Discharge (Opeartion)	C=150pF, R=330 Ω, 5 points/panel Air:±8KV, 5 times; Contact: ±4KV, 5 times; (Environment: 15°C ~ 35°C, 30% ~ 60%, 86Kpa ~ 106Kpa)	IEC61000-4-2 GB/T17626.2-1998
8	Vibration (Non-operation)	Frequency range: 1~55Hz, Stroke: 1.mm, Sweep: 1Hz~55Hz~3.5Hz 2 hours for each direction of X .Y. Z. (package condition)	IEC60068-2-6 GB/T2423.5-1995
10	Package Drop Test	Height: 80 cm, 1 corner, 3 edges, 6 surfaces	IEC60068-2-32 GB/T2423.8-1995

Note: 1. T<sub>s</sub> is the temperature of panel's surface.

2. T<sub>a</sub> is the ambient temperature of sample.



# Mechanical Drawing



# TFT-LCD Module Inspection Criteria

## Scope

The incoming inspection standards shall be applied to TFT - LCD Modules (hereinafter Called "Modules") that supplied by Midas Displays.

## Incoming Inspection

The customer shall inspect the modules within twenty calendar days of the delivery date (the "inspection period") at its own cost. The result of the inspection (acceptance or rejection) shall be recorded in writing, and a copy of this writing will be promptly sent to The seller, If the results of the inspecting from buyer does not send to the seller within twenty Calendar days of the delivery date. The modules shall be regards as acceptance. Should the customer fail to notify the seller within the inspection period, the buyers Right to reject the modules shall be lapsed and the modules shall be deemed to have Been accepted by the buyer


## Inspection Sampling

- 3.1. Lot size: Quantity per shipment lot per model
- 3.2. Sampling type: Normal inspection, Single sampling
- 3.3. Inspection level: II
- 3.4. Sampling table: MIL-STD-105E
- 3.5. Acceptable quality level (AQL )  
Major defect: AQL=0.65 Minor defect: AQL=1.00

## Inspection Conditions

- 4.1 Ambient conditions:
  - a. Temperature: Room temperature  $25 \pm 5^{\circ}\text{C}$
  - b. Humidity:  $(60 \pm 10) \% \text{RH}$
  - c. Illumination: Single fluorescent lamp non-directive (300 to 700 Lux)
- 4.2 Viewing distance  
The distance between the LCD and the inspector's eyes shall be at least  $35 \pm 5$  cm.
- 4.3 Viewing Angle  
U/D:  $45^{\circ} / 45^{\circ}$  , L/R:  $45^{\circ} / 45^{\circ}$





## 5 Inspection Criteria

Defects are classified as major defects and minor defects according to the degree of Defectiveness defined herein.

### 5.1 Major defect



Item No	Items to be inspected	Inspection Standard
5.1.1	All functional defects	1) No display 2) Display abnormally 3) Short circuit 4) line defect
5.1.2	Missing	Missing function component
5.1.3	Crack	Glass Crack

### 5.2 Minor defect



Item No	Items to be inspected	Inspection standard
5.2.1	Spot Defect Including Black spot White spot Pinhole Foreign particle Polarizer dirt	For dark/white spot is defined $\varphi = (x+y) / 2$
		<table border="1" style="width: 100%;"> <tr> <td style="text-align: center;">Size <math>\varphi</math>(mm)</td> <td style="text-align: center;">Acceptable Quantity</td> </tr> </table>
Size $\varphi$ (mm)	Acceptable Quantity	






		$\phi \leq 0.2$	Ignore			
		$0.2 < \phi \leq 0.5$	3			
		$0.5 < \phi$	Not allowed			
5.2.2	Line Defect Including Black line White line Scratch	Define:				
						
		Width(mm) Length(mm)		Acceptable Quantity		
		$W \leq 0.03$		Ignore		
		$0.03 < W \leq 0.04$ $L \leq 5.0$		4		
$0.04 < W, \text{ or } L > 5.0$		Not allowed				
5.2.3	Polarizer Dent/Bubble	Size $\phi$ (mm)		Acceptable Quantity		
		$\phi \leq 0.25$		Ignore		
		$0.25 < \phi \leq 0.5$		3		
		$0.5 < \phi$		Not allowed		
Total QTY		3				
5.2.4	Electrical Dot Defect	Bright and Black dot define:				
						
		Two Adjacent Dot				
		Inspection pattern: Full white, Full black, Red, green and blue screens				
Item		Acceptable Quantity				
		I	O	Total		



		<b>Black dot defect</b>	<b>2</b>	<b>3</b>	<b>4</b>
		<b>Bright dot defect</b>	<b>0</b>	<b>3</b>	<b>3</b>
		<b>Total Dot</b>	<b>2</b>	<b>4</b>	<b>5</b>
		<b>3% Bright Dot is allowed</b>			
<b>5.2.5</b>	<b>Glass defect</b>				
		<b>1. Corner Fragment:</b>			
		<b>Size(mm)</b>		<b>Acceptable Quantity</b>	
		$X \leq 3\text{mm}$ $Y \leq 1\text{mm}$ $Z \leq T$		<b>Ignore</b> <b>T: Glass thickness</b> <b>X: Length</b> <b>Y: Width</b> <b>Z: thickness</b>	
		<b>2. Side Fragment:</b>			
					
<b>Size(mm)</b>		<b>Acceptable Quantity</b>			
$X \leq 5.0\text{mm}$ $Y \leq 1\text{mm}$ $Z \leq T$		<b>T: Glass thickness</b> <b>X: Length</b> <b>Y: Width</b> <b>Z: thickness</b>			





### I area & O area

- Note:
- 1). Dot defect is defined as the defective area of the dot area is larger than 50% of the dot area.
  - 2). The distance between two bright dot defects (red, green, blue, and white) should be larger than 15mm.
  - 3). The distance between black dot defects or black and bright dot defects should be more than 5mm apart.
  - 4). Polarizer bubble is defined as the bubble appears on active display area. The defect of polarizer bubble shall be ignored if the polarizer bubble appears on the outside of active display area.

### Mechanics specification

As for the outside dimension, weight of the modules, please refer to product specification  
For more details

## Precautions for Use of LCD modules

### Handling Precautions

1.1. The display panel is made of glass. Do not subject it to a mechanical shock by dropping it from a high place, etc.

1.2. If the display panel is damaged and the liquid crystal substance inside it leaks out, be sure not to get any in your mouth, if the substance comes into contact with your skin or clothes, promptly wash it off using soap and water.



1.3. Do not apply excessive force to the display surface or the adjoining areas since this may cause the color tone to vary.

1.4. The polarizer covering the display surface of the LCD module is soft and easily scratched. Handle this polarizer carefully.

1.5. If the display surface is contaminated, breathe on the surface and gently wipe it with a soft dry cloth. If still not completely clear, moisten cloth with one of the following solvents:

- Isopropyl alcohol
- Ethyl alcohol

Solvents other than those mentioned above may damage the polarizer. Especially, do not use the following:

- Water
- Ketene

1.6. Do not attempt to disassemble the LCD Module.

1.7. If the logic circuit power is off, do not apply the input signals.

1.8. To prevent destruction of the elements by static electricity, be careful to maintain an optimum work environment.

1.8.1. Be sure to ground the body when handling the LCD Modules.

1.8.2. Tools required for assembly, such as soldering irons, must be properly ground.

1.8.3. To reduce the amount of static electricity generated, do not conduct assembly and other work under dry conditions.

1.8.4. The LCD Module is coated with a film to protect the display surface. Be care when peeling off this protective film since static electricity may be generated.

## **Storage Precautions**

2.1. When storing the LCD modules, avoid exposure to direct sunlight or to the light of fluorescent lamps.

2.2. The LCD modules should be stored under the storage temperature range. If the LCD modules will be stored for a long time, the recommend condition is:

Temperature : 0°C ~ 40°C Relatively humidity: ≤80%

2.3. The LCD modules should be stored in the room without acid, alkali and harmful gas.

## **Transportation Precautions**

The LCD modules should be no falling and violent shocking during transportation, and also should avoid excessive press, water, damp and sunshine.

