# E3Z


CE

## The Standard for Photoelectric Sensors with a Secure Track Record of One Million Sold Yearly.

- Long sensing distance of 30 m for Through-beam Models, 4 m for Retro-reflective Models, and 1 m for Diffuse-reflective Models.
- $\bullet$  Mechanical axis and optical axis offset of less than  $\pm 2.5^\circ$  simplifies optical axis adjustment.
- High stability with unique algorithm that prevents interference of external light.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.




## Features

# Industry's Top-level Sensing Distance with Built-in Amplifier

A separately sold filter is available to prevent mutual interference for Through-beam Models with red lights sources and a sensing distance of 10 m. Reflective Models include functionality to prevent mutual interference (up to 2 sensors).

Long-distance, Through-beam Sensors with a detection distance of 30 m (response time: 2 ms) are also available.



## Low-temperature Operation for Applications in Cold-storage Warehouses


A wider ambient operating range from -40 to 55°C (main models with connectors). We also provide Sensor I/O Connectors with PUR Cables for high resistance to cold environments.

## Improved Matching of Optical Axis and Mechanical Axis for Through-beam Models and Retro-reflective Models

The offset between the optical axis and the mechanical axis is kept within  $\pm 2.5^{\circ}$ , so the optical axis can be accurately set simply by mounting the Sensor according to the mechanical axis.

## Sensor Protection against Incorrect Wiring

The Sensor includes output reverse polarity protection. (A diode to protect against reverse polarity is added to the output line.)



axis


Protection for NPN output models

circuit

## Complete Compliance with the EU's RoHS Directive

Lead, mercury, cadmium hexachrome, polybrominated biphenyl (PBB), and polybrominated diphenyl ether (PBDE) have all been eliminated. Also, burnable polyethylene packaging has been used.





0 V

## **Ordering Information**

Sensing method	Appearance	Connection method	Sensing distance	Mo	odel
Sensing memou	Appearance	Someonon meniou		NPN output	PNP output
		Pre-wired (2 m)	(C) 15 m	<b>E3Z-T61 2M *4 *5</b> Emitter E3Z-T61-L 2M Receiver E3Z-T61-D 2M	<b>E3Z-T81 2M *4 *5</b> Emitter E3Z-T81-L 2M Receiver E3Z-T81-D 2M
		Standard M8 connector	∑15 m	E3Z-T66 Emitter E3Z-T66-L Receiver E3Z-T66-D	E3Z-T86 Emitter E3Z-T86-L Receiver E3Z-T86-D
Through-beam (Emitter + Receiver) *3	لیے ایے	Pre-wired (2 m)	10.55	<b>E3Z-T61A 2M *4</b> Emitter E3Z-T61-A-L 2M Receiver E3Z-T61-A-D 2M	<b>E3Z-T81A 2M *4</b> Emitter E3Z-T81-A-L 2M Receiver E3Z-T81-A-D 2M
		Standard M8 connector	10 m	E3Z-T66A Emitter E3Z-T66-A-L Receiver E3Z-T66-A-D	E3Z-T86A Emitter E3Z-T86-A-L Receiver E3Z-T86-A-D
		Pre-wired (2 m)	(C) 20m	<b>E3Z-T62 2M *4</b> Emitter E3Z-T62-L 2M Receiver E3Z-T62-D 2M	E3Z-T82 2M Emitter E3Z-T82-L 2M Receiver E3Z-T82-D 2M
		Standard M8 connector	\$30m	E3Z-T67 Emitter E3Z-T67-L Receiver E3Z-T67-D	E3Z-T87 Emitter E3Z-T87-L Receiver E3Z-T87-D
Retro-reflective with		Pre-wired (2 m)	4 m *2	E3Z-R61 2M *4 *5	E3Z-R81 2M *4 *5
MSR function	*	1 Standard M8 connector	(100 mm)	E3Z-R66	E3Z-R86
		Pre-wired (2 m)	5 to 100 mm	E3Z-D61 2M *4	E3Z-D81 2M *4 *5
		Standard M8 connector	(wide view)	E3Z-D66	E3Z-D86
Diffuse-reflective		Pre-wired (2 m)	1 m	E3Z-D62 2M *4 *5	E3Z-D82 2M *4 *5
		Standard M8 connector	1 m	E3Z-D67	E3Z-D87
		Pre-wired (2 m)	90±30 mm	E3Z-L61 2M *4 *5	E3Z-L81 2M *4 *5
		Standard M8 connector	(narrow beam)	E3Z-L66	E3Z-L86
		Pre-wired (2 m)	20 to 40 mm (BGS min setting) 20 to 200 mm (BGS max setting)	E3Z-LS61 2M *4	E3Z-LS81 2M *4
Distance-settable Refer to <b>E3Z-LS</b> .		Standard M8 Connector	40 min. Incident threshold (FGS min setting) 200 min. Incident threshold (FGS max setting)	E3Z-LS66	E3Z-LS86
		Pre-wired (2 m)	2 to 20 mm (BGS min setting)		E3Z-LS83 2M *5
		Standard M8 connector	2 to 80 mm (BGS max setting	) <b>E3Z-LS68</b>	E3Z-LS88
	1 axis	Pre-wired (2 m)		E3Z-G61 2M *4 *5	E3Z-G81 2M *4 *5
Slit-type Through- beam	2 axes		25 mm	E3Z-G62 2M *4	E3Z-G82 2M *4
Refer to E3Z-G.	1 axis	Pre-wired M8 connector		E3Z-G61-M3J	E3Z-G81-M3J
	2 axes			E3Z-G62-M3J	E3Z-G82-M3J
Limited-reflective for		Pre-wired (2 m)	30±20 mm	E3Z-L63 2M	E3Z-L83 2M
transparent glasses		Standard M8 connector		E3Z-L68	E3Z-L88
<b>.</b>		Pre-wired (2 m)	500 mm (80 mm)	E3Z-B61 2M	E3Z-B81 2M *4
Retro-reflective with- out MSR function for	₹1	Standard M8 connector		E3Z-B66	E3Z-B86
clear, plastic bottles		Pre-wired (2 m)	2 m (500 mm)	E3Z-B62 2M *4	E3Z-B82 2M *4
		Standard M8 connector		E3Z-B67	E3Z-B87

\*1. The Reflector is sold separately. Select the Reflector model most suited to the application.
 \*2. The sensing distance specified is possible when the E39-R1S is used. Values in parentheses indicate the minimum required distance between the Sensor and Reflector.
 \*3. Through-beam Sensors are normally sold in sets that include both the Emitter and Receiver.
 \*4. M12 Standard Pre-wired Connector Models are also availavble. When ordering, add "-M1J 0.3M" to the end of the model number (e.g., E3Z-T61-M1J 0.3M). The cable is 0.3 m long.
 \*5. M12 Pre-wired Smartclick Connector Models are also availavble. When ordering, add "-M1TJ 0.3M" to the end of the model number (e.g., E3Z-T61-M1TJ 0.3M). The cable is 0.3 m long.

Sensing method	Appearance	Connection method	Son	cina di	stanco		Model		
Sensing method	Appearance	Connection method	Sensing distance			NPN output		PNP output	
Through-beam (Emitter + Receiver) *3		Pre-wired (2 m)				Emitter Receive	<b>'61K 2M *4</b> E3Z-T61K-L 2M r E3Z-T61K-D 2M	Emitter	8 <b>1K 2M *4</b> E3Z-T81K-L 2M E3Z-T81K-D 2M
		Pre-wired M8 connector			<mark>}∑</mark> 15 m	E3Z-I Emitter	<b>61K-M3J 0.3M</b> E3Z-T61K-L-M3J 2M r E3Z-T61K-D-M3J 2M	E3Z-T Emitter Receiver	<b>31K-M3J 0.3M</b> E3Z-T81K-L-M3J 2M E3Z-T81K-D-M3J 2M
Retro-reflective with	<b>∫ → 1</b>	Pre-wired (2 m)			*2	E3Z-F	R61K 2M *4	E3Z-R	81K 2M
MSR function		Pre-wired M8 connector		3 m	1 (150 mm)	E3Z-F	R61K-M3J 0.3M	E3Z-R	81K-M3J 0.3M
		Pre-wired (2 m)		, í		E3Z-D	061K 2M *4	E3Z-D	B1K 2M
Diffuse-reflective	<b>_</b>	Pre-wired M8 connector	5 to 100	0 mm (w	ide view)	E3Z-D	E3Z-D61K-M3J 0.3M		81K-M3J 0.3M
Diruse-renective		Pre-wired (2 m)				E3Z-D	062K 2M *4	E3Z-D	B2K 2M
		Pre-wired M8 connector	<b></b> 1 m			E3Z-D	062K-M3J 0.3M	E3Z-D	82K-M3J 0.3M

\*1. The Reflector is sold separately. Select the Reflector model most suited to the application.
\*2. The sensing distance specified is possible when the E39-R1S is used. Values in parentheses indicate the minimum required distance between the Sensor and Reflector.
\*3. Through-beam Sensors are normally sold in sets that include both the Emitter and Receiver.

\*4. M12 Standard Pre-wired Connector Models are also available.
 When ordering, add "-M1J 0.3M" to the end of the model number (e.g., E3Z-T61-M1J 0.3M). The cable is 0.3 m long.

## Accessories (Order Separately)

Slit (A Slit is not provided with Through-beam Sensors) Order a Slit separately if required. [Refer to Dimensions on page 16.]

Slit width	Sensing	distance	Minimum detectable object	Model	Contents	
Siit width	E3Z-T	E3Z-T A	(Reference value)	Woder	Contents	
0.5-mm dia.	50 mm	35 mm	0.2-mm dia.	E39-S65A		
1-mm dia.	200 mm	150 mm	0.4-mm dia.	E39-S65B	One set	
2-mm dia.	800 mm	550 mm	0.7-mm dia.	E39-S65C	(contains Slits for	
0.5  imes 10  mm	1 m	700 mm	0.2-mm dia.	E39-S65D	both the Emitter and	
$1 \times 10 \text{ mm}$	2.2 m	1.5 m	0.5-mm dia.	E39-S65E	Receiver)	
$2 \times 10 \text{ mm}$	5 m	3.5 m	0.8-mm dia.	E39-S65F	]	

Reflectors (Reflector required for Retroreflective Sensors) A Reflector is not provided with the Sensor. Be sure to order a Reflector separately. [Refer to Dimensions on E39-L/E39-S/E39-R]

		S						
	E32	Z-R	E3Z-R□K E3Z-B□1/-B□6		E3Z-B□2/-B□7			
Name	Rated value (sensing distance of 15 m)	Reference value (sensing distance of 10 m)	Rated value	Rated value	Rated value	Model	Quantity	Remarks
	3 m (100 mm)		2 m (100 mm)			E39-R1	1	
	4 m (100 mm)		3 m (150 mm)	500 mm (80 mm)	2 m (500 mm)	E39-R1S	1	Retro-reflective     models are not
Reflector		5 m (100 mm)				E39-R2	1	
		2.5 m (100 mm)				E39-R9	1	
		3.5 m(100 mm)				E39-R10	1	provided with
Fog Preventive Coating		3 m (100 mm)		500 mm (80 mm)	2 m (500 mm)	E39-R1K	1	• The MSR function
Small Reflector		1.5 m (50 mm)				E39-R3	1	is enabled.
		700 mm (150 mm)				E39-RS1	1	
Tape Reflector		1.1 m (150 mm)				E39-RS2	1	
		1.4 m (150 mm)				E39-RS3	1	

Note: 1. If you use the Reflector at any distance other than the rated distance, make sure that the stability indicator lights properly when you install the Sensor. 2. Refer to *Reflectors* on *E39-L/E39-S/E39-R* for details. \* Values in parentheses indicates the minimum required distance between the Sensor and Reflector.

Mutual Interference Protection Filter A Filter is not provided with the Sensor (for the through-beam E3Z-TUA). Order a Filter separately if required.

Sensing distance	Appearance/Dimensions	Model	Quantity	Remarks
3 m		E39-E11	Two sets each for the Emitter and Receiver (total of four pieces)	Can be used with the E3Z-T A Through- beam models. The arrow indicates the direc- tion of polarized light. Mutual interference can be prevented by altering the direction of polarized light from or to adjacent Emitters and Receivers.

Note: The polarization directions of the Filters are offset by 90° to prevent interference. When you install the Emitter and Receiver, install them at the same angle to maintain this offset.

#### Mounting Brackets A Mounting Bracket is not enclosed with the Sensor. Order a Mounting Bracket separately if required. [Refer to Dimensions on E39-L/E39-S/E39-R]

Appearance	Model (material)	Quantity	Remarks	Appearance	Model (material)	Quantity	Remarks
	E39-L153 (SUS304) *1	1			E39-L98 (SUS304) *2	1	Metal Protective Cover Bracket
No.	E39-L104 (SUS304) *1	1	Mounting Brackets		E39-L150 (SUS304)	1	(Sensor adjuster)
	E39-L43 (SUS304) *2	1	Horizontal Mounting Brackets		E39-L151	1	Easily mounted to the aluminum frame rails of conveyors and easily adjusted.
	E39-L142 (SUS304) *2	1	Horizontal Protective Cover Bracket		(SUS304)	1	For left to right adjust- ment
e l	E39-L44 (SUS304)	1	Rear Mounting Bracket		E39-L144 (SUS304) *2	1	Compact Protective Cover Bracket (For E3Z only)

Note: 1. When using Through-beam models, order one bracket for the Receiver and one for the Emitter.
 2. Refer to *Mounting Brackets* on *E39-L/E39-S/E39-R* for details.
 \*1. Cannot be used for Standard Connector models with mounting surface on the bottom. In that case, use Pre-wired Connector models.

\*2. Cannot be used for Standard Connector models.

#### Sensor I/O Connectors (Sockets on One Cable End)

(Models for Connectors and Pre-wired Connectors: A Connector is not provided with the Sensor. Be sure to order a Connector separately.) [Refer to Dimensions for XS3.]

Size	Cable	Арре	arance	Cable type		Model
M8 *1		Otroinht *0		2 m	- 4-wire	XS3F-M421-402-A
	Ctandard	Straight *3	C Without	5 m		XS3F-M421-405-A
	Standard	L-shaped *3 *4		2 m		XS3F-M422-402-A
				5 m		XS3F-M422-405-A
		Straight *3	C Martin	2 m	- 4-wire	XS3F-M421-402-L
Mo	PUR (Dahuwa			5 m		XS3F-M421-405-L
M8	(Polyure- thane) cable *2	L-shaped *3 *4		2 m		XS3F-M422-402-L
	,			5 m	-	XS3F-M422-405-L

Note: When using Through-beam models, order one connector for the Receiver and one for the Emitter. \*1. Refer to Introduction to Sensor I/O Connectors/Sensor Controllers for details.

\*2. The Sensor can be used in low-temperature environments (-25°C to -40°C). Do not use the Sensor in locations that are subject to oil.

\*3. The connector will not rotate after connecting.

\*4. The cable is fixed at an angle of 180° from the sensor emitter/receiver surface.

## **Ratings and Specifications**

			Sensing method		Through-beam	1	Retro-reflective MSR function		Diffuse-r	eflective	(Narrow- beam Models)
	Γ	NPN	Pre-wired	E3Z-T61	E3Z-T62	E3Z-T61A	E3Z-R61		E3Z-D61	E3Z-D62	E3Z-L61
		out- put	Connector (M8)	E3Z-T66	E3Z-T67	E3Z-T66A	E3Z-R66		E3Z-D66	E3Z-D67	E3Z-L66
Mo	odel	PNP	Pre-wired	E3Z-T81	E3Z-T82	E3Z-T81A	E3Z-R81		E3Z-D81	E3Z-D82	E3Z-L81
Item		out- put	Connector (M8)	E3Z-T86	E3Z-T87	E3Z-T86A	E3Z-R86		E3Z-D86	E3Z-D87	E3Z-L86
Sensing dis	tance	!		15 m	30 m	10 m	4 m (100 mm) *1 (when using E39-1 3 m (100 mm) *1 (when using E39-		100 mm (white paper: 100 × 100 mm)	1 m (white paper: 300 × 300 mm)	90 + 30 mm (white paper, 100 x 100 mm)
Spot diamet	ter (re	feren	ce value)								(2.5 dia. and sensing dis- tance of 90 mm)
Standard se	ensing	j obje	ct	Opaque: 12-n	Opaque: 12-mm dia. min. Opaque: 75-mm dia. min						
	Minimum detectable object (reference value)							1			0.1 mm (cop- per wire)
Differential travel								20% max. of sett	ing distance	Refer to <i>Engi- neering data</i> on page 8.	
Directional angle				Both emitter a	and receiver: 3	to 15°	2 to 10°				
Light source	Light source (wavelength)		jth)	Infrared LED	(870 nm)	Red LED (660 nm)	Red LED (660 nm	1)	Infrared LED (86	0 nm)	Red LED (650 nm)
Current consumption			35 mA max. ( er: 20 mA ma	Emitter: 15 mA x.)	max., Receiv-	· · · · · · · · · · · · · · · · · · ·					
Protection circuits				Output short-	ver supply polar circuit protectio polarity protec	n, and Re-	<ol> <li>Reversed power supply polarity protection, Output short-circuit protect Mutual interference prevention, and Reversed output polarity protection</li> </ol>				
Response ti	Response time			Operate or reset: 1 ms max.	Operate or reset: 2 ms max.	Operate or re	eset: 1 ms max.				
Degree of p	rotect	ion		IEC, IP67							
Connection	meth	od		Pre-wired cable (standard length: 2 m and 0.5 m), Connector (M8)							
Weight	-> +		rired cable (2 m)	Approx. 120 g Approx. 65 g							
(packedstat	-	Conn	ector	Approx. 30 g Approx. 20 g PBT (polybutylene terephthalate)							
Material	-	Case Lens		Modified poly		late)	Methacrylic resin Modified polyarylate				
		Lens		woulled poly	,						
		Se	ensing method		Retro-			ic bottles (without MSR function)			
	Мос	del	NPN output		-B61	E32	Z-B66		E3Z-B62		Z-B67
Item			PNP output	-	-B81		Z-B86		E3Z-B82		Z-B87
Sensing di					mm) *1 (usir			m (50	00 mm) *1 *2 (u	ising E39-R1S)	
Standard sensing object			500-ml (65-mm dia.) transparent round plastic bottles								
		•	•	``		•					
Light sour	ce (w	/avel	ength)	Red LED (6	,						
	ce (w	/avel	ength)	Red LED (6 30 mA max.	,		·				
Light sour	ce (w onsur	vavel nptio	ength)	Red LED (6 30 mA max. Reversed po	,	olarity protec	tion, Output shor	t-circu	uit protection, M	utual interferen	ce prevention,
Light sour Current co	rce (w onsur i circi	vavel nptio uits	ength)	Red LED (6 30 mA max. Reversed po and Reverse	ower supply p	olarity protec	tion, Output shor	t-circı	uit protection, M	utual interferen	ce prevention,
Light sour Current co Protection Response	ce (w onsur circu time	vavel nptio uits	n	Red LED (6 30 mA max. Reversed po and Reverse	ower supply p ed output pole	olarity protec	tion, Output shor	t-circu	uit protection, M	utual interferen	ce prevention,
Light sour Current co Protection Response	rce (w onsur circu time prote	vavel nptio uits	n	Red LED (6 30 mA max. Reversed po and Reverse Operate or r IEC, IP67	ower supply p ed output pola reset: 1 ms m ble (standard	olarity protec arity protectic ax.	tion, Output shor	Pre-wir	uit protection, M ed cable (standa 2 m and 0.5 m)	ard	ce prevention,
Light sour Current co Protection Response Degree of Connectio Weight	rce (w onsur circu time prote	vavel nptio uits ection	n	Red LED (6 30 mA max. Reversed po and Reverse Operate or r IEC, IP67 Pre-wired ca	ower supply p ed output pola reset: 1 ms m ble (standard und 0.5 m)	olarity protec arity protectic ax.	tion, Output shor	Pre-wir	ed cable (standa	ard	· · ·
Light sour Current co Protection Response Degree of Connectio Weight (packed	rce (w onsur circu time prote n me Pre-v	vavel nptio uits ection thod wired	n	Red LED (6 30 mA max. Reversed po and Reverse Operate or r IEC, IP67 Pre-wired ca length: 2 m a	ower supply p ed output pola reset: 1 ms m ble (standard and 0.5 m)	olarity protec arity protectic ax.	tion, Output shor	Pre-wir	ed cable (standa	ard	· · ·
Light sour Current co Protection Response Degree of Connectio Weight (packed state)	rce (w onsur circu time prote n me Pre-v	vavelo mptio uits ection thod wired dard	cable (2 m)	Red LED (6 30 mA max. Reversed po and Reverse Operate or r IEC, IP67 Pre-wired ca length: 2 m a Approx. 65 g Approx. 20 g	ower supply p ed output pola reset: 1 ms m ble (standard and 0.5 m)	olarity protect arity protection ax.	tion, Output shor	Pre-wir	ed cable (standa	ard	· · ·

\*1. Values in parentheses indicate the minimum required distances between the Sensors and Reflectors.
 \*2. Plastic bottles must pass with the minimum clearance of 500 mm.

	Sensing method	Transparent glass Limited-reflection	ve (for transparent object detection )				
Model	NPN output	E3Z-L63	E3Z-L68				
Item	PNP output	E3Z-L83	E3Z-L88				
Sensing distanc	e	30±20 mm (transparent glasses 100 × 100 mm)					
Spot diameter (r	eference value)	2-mm dia. min. (at sensing distance of 30 mm)					
Minimum detect (reference value		0.1 mm dia. (copper wire)					
Light source (wa	avelength)	Red LED (660 nm)					
Current consum	ption	30 mA max.					
Protection circu	its	Power supply reverse polarity protection, Output short-circuit protection, Mutual interference prevention, Reverse output polarity protection					
Response time		Operate or reset: 1 ms max.					
Degree of protect	ction	IEC, IP67					
Connection met	hod	Pre-wired (standard length: 2 m)	M8 connector				
Weight	Pre-wired cable (2 m)	Approx. 65 g					
(packed state)	Standard Connector	Approx. 20 g	Approx. 20 g				
Material	Case	PBT (polybutylene terephthalate)					
wateriai	Lens	Modified polyarylate					

#### **Oil-resistant**

			Sensing method	Through-beam	Retro-reflective	Diffuse-	reflective		
		NPN	Pre-wired Models	E3Z-T61K	E3Z-R61K	E3Z-D61K	E3Z-D62K		
	Medel	out- put	M8 Pre-wired connector	E3Z-T61K-M3J	E3Z-R61K-M3J	E3Z-D61K-M3J	E3Z-D62K-M3J		
	Model	PNP	Pre-wired Models	E3Z-T81K	E3Z-R81K	E3Z-D81K	E3Z-D82K		
Item		out- put	M8 Pre-wired connector	E3Z-T81K-M3J	E3Z-R81K-M3J	E3Z-D81K-M3J	E3Z-D82K-M3J		
Sensing distance		15 m	3 m (150 mm) * (when using E39-R1S) 2 m (100 mm) * (when using E39-R1)	100 mm (white paper: $100 \times 100$ mm)	1 m (white paper: 300 × 300 mm)				
Standard sensing object			ect	Opaque: 12-mm dia. min.	Opaque: 75-mm dia. min.				
Differenti	ial trave	el		-		20% max. of setting distan	се		
Directional angle				Both emitter and receiver: 3 to $15^{\circ}$	2 to 10°				
Light sou	urce (wa	avelen	gth)	Infrared LED (870 nm)	Red LED (660 nm)	Infrared LED (860 nm)			
Current c	consum	ption		35 mA max. (Emitter: 15 mA max., Receiver: 20 mA max.)	30 mA max.				
Protectio	on circu	its		Reversed power supply polarity protection, Output short-circuit protection, and Reversed output po- larity protection	Reversed power supply polarity protection, Output short-circuit protection, Mutual in terference prevention, and Reversed output polarity protection				
Respons	e time			Operate or reset: 1 ms max.					
Degree o	f prote	ction		IP67 (IEC), Oil resistant mo	odels: IP67 (IEC) (in-house s	tandards: oilproof), excludin	g cables and connectors		
Connecti	on met	hod		Pre-wired cable (standard I	ength: 2 m), M8 Pre-wired C	onnector			
Weight (packed	Pre-wi	red ca	ble (2 m)	Approx. 120 g	Approx. 65 g				
state)	Conne	ctor (I	M8, 4 pins)	Approx. 50 g	Approx. 30 g				
Material	Case			PBT (polybutylene terephth	alate)				
Material	Lens			Modified polyarylate	Methacrylic resin	Modified polyarylate			


\* Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

#### Common


Power supply voltage	12 to 24 VDC±10%, ripple (p-p): 10% max.					
Control output	Load power supply voltage: 26.4 VDC max., Load current: 100 mA max. Residual voltage: Load current of less than 10 mA: 1 V max. Load current of 10 to 100 mA: 2 V max. Open collector output (NPN/PNP depending on model) Light-ON/Dark-ON selectable					
Sensitivity adjustment	One-turn adjuster					
Ambient illumination (Receiver side)	Incandescent lamp: 3,000 lx max. Sunlight: 10,000 lx max.					
Ambient temperature range	Operating: -25 to 55°C, Some connector models: -40°C to 55°C * (with no icing or condensation) Storage: -40 to 70°C (with no icing or condensation)					
Ambient humidity range	Operating: 35% to 85%, Storage: 35% to 95% (with no condensation)					
Insulation resistance	20 MΩ min. at 500 VDC					
Dielectric strength	1,000 VAC, 50/60 Hz for 1 min					
Vibration resistance	Destruction: 10 to 55 Hz, 1.5 mm double amplitude for 2 hours each in X, Y, and Z directions					
Shock resistance	Destruction: 500 m/s <sup>2</sup> 3 times each in X, Y, and Z directions					
Indicator	Operation indicator (orange) Stability indicator (green) Through-beam Emitter has power indicator (orange) only.					
Accessories	Instruction manual (Neither Reflectors nor Mounting Brackets are provided with any of the above models.)					

\* The ambient temperature range during operation for connector models depends on the model. For the E3Z-T66/T86/R86/R86, the range is -40°C to 55°C. For the E3Z-D66/D86/D67/D87, the range is -30°C to 55°C. For other connector models, the range is -25°C to -55°C. The sensing distance for Retro-reflective Models (E3Z-R66/R86) between -40°C to -25°C, however, will be as follows (not the values in the table): With E39-R1S: 3 m (100 mm), With E39-R1: 2 m (100 mm). Also, use the XS3F-M42\_-4\_\_-L Sensor I/O Connector (PUR cable) for applications between -25°C to -40°C. (Refer to page 4.)


## Parallel Operating Range




Through-beam Models E3Z-T 1(T 6) and Slit (A Slit is mounted to the Emitter and Receiver.)




E3Z-B 1/B 6 + E39-R1S Reflector (Order Separately)












E3Z-T A and Slit (A Slit is mounted to the Emitter and Receiver.)









Retro-reflective Models


E3Z-R 1(R 6) and Reflector



#### E3Z-B□2/B□7 + E39-R1S Reflector (Order Separately)





#### **Operating Range**



#### **Excess Gain vs. Set Distance**


## **Through-beam Models**





#### **Diffuse-reflective Models**

### E3Z-D2(D7)



## **Diffuse-reflective Models** E3Z-D\_2(D\_7)

**Retro-reflective Models** 

Excess gain ratio

10


0.1

E3Z-R 1(R 6) and Reflector


E39-R9

9-R3


E39-R1



#### Narrow-beam Reflective Models E3Z-L 1(L 6)



### **Diffuse-reflective Models** E3Z-D\_1(D\_6)



#### Narrow-beam Reflective Models E3Z-L 1(L 6)


E39-R1K

E39-B10

E39-R1S


E39-R2

Distance (m)




## Limited reflective Models

## E3Z-L\_3(L\_8)




#### **Excess Gain vs. Set Distance**

#### E3Z-B 1/B 6 + E39-R1S **Reflector (Order Separately)**



# **Reflector (Order Separately)** Excess gain ratio


E3Z-B2/B7 + E39-R1S



## Sensing Object Size vs. Sensing Distance


### **Diffuse-reflective Models**

E3Z-D\_1(D\_6)




#### **Spot Diameter vs. Sensing Distance**


## Narrow-beam Reflective Models E3Z-L 1(L 6)



## **Diffuse-reflective Models**




#### **Narrow-beam Reflective Models** E3Z-L 1(L 6)



#### **Differential Travel vs. Sensing Distance**

Narrow-beam Reflective Models E3Z-L 1(L 6)



## I/O Circuit Diagrams

#### **NPN Output**

Model*	Operation mode	Timing charts	Operation selector	Output circuit
E3Z-T61(K) E3Z-T66 E3Z-T62 E3Z-T67 E3Z-T61A E3Z-T66A	Light-ON	Incident light No incident light Operation ON indicator OFF Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown (1) and black (4) leads)	L side (LIGHT ON)	Through-beam Receivers, Retro-reflective Models, Diffuse-reflective Models, Limited reflective Models.
E3Z-R61(K) E3Z-R66 E3Z-D61(K) E3Z-D66 E3Z-D62(K) E3Z-D67 E3Z-L61 E3Z-L66	Dark-ON	Incident light No incident light Operation ON indicator OFF Output ON transistor OFF Load Operate (e.g., relay) Reset (Between brown (1) and black (4) leads)	D side (DARK ON)	Connector Pin Arrangement
E3Z-L66 E3Z-B61 E3Z-B66 E3Z-B62 E3Z-B67 E3Z-L63 E3Z-L68	Through-beam	Emitter	B	Connector Pin Arrangement Connector Pin Arrangement 12 to 24 VDC Pins 2 and 4 are not used.


#### **PNP Output**

Model*	Operation mode	Timing charts	Operation selector	Output circuit
E3Z-T81(K) E3Z-T86 E3Z-T82 E3Z-T87 E3Z-T81A E3Z-T86A E3Z-R86 E3Z-D81(K) E3Z-D86 E3Z-D82(K) E3Z-D87 E3Z-L81 E3Z-L86 E3Z-B81 E3Z-B81 E3Z-B82 E3Z-B87 E3Z-L83 E3Z-L83 E3Z-L88	Light-ON	Incident light No incident light Operation ON indicator OFF Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue (3) and black (4) leads)	L side (LIGHT ON)	Through-beam Receivers, Retro-reflective Models, Diffuse-reflective Models, Limited reflective Models.
	Dark-ON	Incident light Operation ON Indicator OFF (orange) Output ON transistor OFF Load Operate (e.g., relay) Reset (Between blue (3) and black (4) leads)	D side (DARK ON)	Connector Pin Arrangement
	Through-beam Emitter		Bin	Le Connector Pin Arrangement 12 to 24 VDC Pins 2 and 4 are not used.

\* Models numbers for Through-beam Sensors (E3Z-TID) are for sets that include both the Emitter and Receiver. The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3Z-T61-L 2M), the model number of the Receiver, by adding "-D" (example: E3Z-T61-D 2M.) Refer to Ordering Information to confirm model numbers for Emitter and Receivers.

#### Plugs (Sensor I/O Connectors)

#### M8 connector



#### Pin arrangement

Classifi- cation	Wire color	Connector pin No.	Application
	Brown	1	Power supply (+V)
DC	White	2	-
	Blue	3	Power supply (0 V)
	Black	4	Output

Note: Pin 2 is not used.

## Nomenclature

Through-beam Models E3Z-T (Receiver) E3Z-T A (Receiver)

Retro-reflective Models E3Z-R

Operation selector

Stability indicator

(green)

Operation indicator (orange) Sensitivity adjuster

Diffuse-reflective Models E3Z-D

Narrow-beam Reflective Models E3Z-L

Limited reflective Models E3Z-L

#### Refer to Warranty and Limitations of Liability.

#### <u> W</u>ARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



### **Precautions for Correct Use**

Do not use the product in atmospheres or environments that exceed product ratings.

#### Wiring


#### **M8 Metal Connector**

- Be sure to connect or disconnect the metal connector after turning OFF the Sensor.
- Hold the connector cover to connect or disconnect the metal connector.
- Secure the connector cover by hand. Do not use any pliers, otherwise the connector may be damaged.
- The proper tightening torque range is between 0.3 and 0.4 N·m. Be sure to tighten the connector securely, otherwise the specified degree of protection may not be maintained or the connector may be disconnected due to vibration.

#### Mounting

#### **Sensor Mounting**

Use M3 screws to mount the sensor and tighten each screw to a maximum torque of 0.53  $N\mbox{-}m.$ 



#### Oil-resistant Models

#### **Oil Resistance**

- Although the E3Z- K Sensors have oil-resistant specifications, performance may be affected by certain types of oil. Refer to the following table.
- E3Z-UDK Sensors are tested for resistance to the oils given in the following table. Refer to the information in the table when deciding which type of oil to use.


Test oil clas- sification	Product name	Kinematic viscosity (mm²/s) at 40°C	рН	
Lubricant	Velocity No.3 (manufactured by Exx- on Mobil)	2.02		
Water insolu- ble machining oil	Yushiron Oil No.2 ac (manufactured by Yushiro Chemical In- dustry Co., Ltd.)	Less than 10	1	
	Yushiroken EC50T-3 (manufactured by Yushiro Chemical In- dustry Co., Ltd.)		7 to 9.5	
Watersoluble	Yushiron Lubic HWC68 (manufactured by Yushiro Chemical In- dustry Co., Ltd.)		7 to 9.9	
machining oil	Gryton 1700D (manufactured by Toho Chemical Industry Co., Ltd.)		7 to 9.2	
	Yushironken S50N (manufactured by Yushiro Chemical In- dustry Co., Ltd.)		7 to 9.8	

- Note: 1. The E3Z maintained a minimum insulation resistance of 100  $M\Omega$  after it was dipped in all the above oils for 240 hours.
  - When using the Sensors in environments subject to oils other than those listed above, use the figures for kinematic viscosity and pH from the table as general guidelines. Additives and other substances contained in oils may affect the E3Z. Be sure to consider this before use.

## **Dimensions**

F37

#### Sensors



\* Models numbers for Through-beam Sensors (E3Z-TIDD) are for sets that include both the Emitter and Receiver. The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3Z-T61-L 2M), the model number of the Receiver, by adding "-D" (example: E3Z-T61-D 2M.) Refer to Ordering Information to confirm model numbers for Emitter and Receivers.

#### **Retro-reflective Models Pre-wired Models** E3Z-R61(K) E3Z-B61 4.5 11.2 E3Z-R81(K) E3Z-B81 Operation Indicator (orange) 7.5 E3Z-D61(K) E3Z-B62 E3Z-D81(K) E3Z-B82 E3Z-D62(K) E3Z-L63 П Operation selector E3Z-D82(K) E3Z-L83 Stability indicator (green) Sensitivity adjuster E3Z-L61 10.8 E3Z-L81 2.1 28 Receiver Lens 7 dia. З M8 Pre-wired Connector (E3Z-T K-M3J) 4 dia. vinyl-insulated round cable 16.7 with 3 conductors, Standard length: 0.3 m 31 8 25.4 Two, M3 Emitter M8 Lens 7 dia. 4 dia. vinyl-insulated round cable with 3 conductors (Conductor cross section: 0.2 mm<sup>2</sup> (AWG24), Insulator diameter:1.1 mm), Standard length: 2 m Specifica-tions Terminal No. +V 1 2

---


0V

Output


3

4

#### **Retro-reflective Models**



Note: The lens for the E3Z-D 1/D 6/L /B is red. The lens for the E3Z-D 2/D 7 is black.



#### **Mounting Brackets**

Refer to E39-R for details.

#### Sensor I/O Connectors

Refer to XS3 for details.

# Terms and Conditions of Sale

- 1. Offer; Acceptance. These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms. Prices: Payment Terms, All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice. Discounts, Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.
- 2
- 3.
- and (ii) Buyer has no past due amounts. Interest. Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the stated terms.
- Orders. Omron will accept no order less than \$200 net billing. Governmental Approvals. Buyer shall be responsible for, and shall bear all 6 costs involved in, obtaining any government approvals required for the impor-tation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or 7. indirectly by Omron for the manufacture, production, sale, delivery, importa-tion, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron. <u>Financial.</u> If the financial position of Buyer at any time becomes unsatisfactory
- 8. <u>Einancial</u> If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liabil-ity and in addition to other remedies) cancel any unshipped portion of Prod-ucts sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts unpaid accounts.
- <u>Cancellation</u>, <u>Etc.</u> Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.
   <u>Force Majeure</u>. Omron shall not be liable for any delay or failure in delivery
- Force majeure. Other shall not be lable for any delay or lating in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.
   Shipping: Delivery. Unless otherwise expressly agreed in writing by Omron: a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship expert in "break down" situations.
- except in "break down" situations. b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall
  - constitute delivery to Buyer; c. All sales and shipments of Products shall be FOB shipping point (unless oth-
- c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
  d. Delivery and shipping dates are estimates only; and
  e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.
  12. <u>Claims</u>. Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier received the Products
- portation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
- <u>Warranties</u>. (a) <u>Exclusive Warranty</u>. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed 13 (b) <u>Limitations</u>. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABIL-

## Certain Precautions on Specifications and Use

- Suitability of Use. Omron Companies shall not be responsible for conformity 1. with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request. Omron will provide application to use of the Froduct. At Buyer's application of use of the product applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Prod-uct in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. the particular Product with respect to Buyers application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given: (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document. (ii) Use in consumer products or any use in significant quantities. (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equip-ment and installicitors cubications of the consumer to construct the construction.

inent, and installations subject to separate industry or government regulations. (iv) Systems, machines and equipment that could present a risk to life or prop erty. Please know and observe all prohibitions of use applicable to this Prod-

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO

ITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or oth-erwise of any intellectual property right. (c) <u>Buyer Remedy</u>. Omron's sole obli-gation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsi-ble for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were prop-erly handled, stored, installed and maintained and not subject to contamina-tion, abuse, misuse or inappropriate modification. Return of any Products by tion, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Compa-nies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See http://www.omron247.com or contact your Omron representative for published information.

- Iished information.
  Limitation on Liability: Etc. OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted. 14
- Indemnities. Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, inves-tigation, litigation or proceeding (whether or not Omron is a party) which arises 15 or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or set-tle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
- rights of another party. <u>Property: Confidentiality.</u> Any intellectual property in the Products is the exclu-sive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly provent disclosure to any third party. 16
- 17
- "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of regulated technology or information. <u>Miscellaneous</u>. (a) <u>Waiver</u>. No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) <u>Assignment</u>. Buyer may not assign its rights hereunder without Omron's written consent. (c) <u>Law</u>. These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) <u>Amendment</u>. These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) Severability. If any provi-18 or waived unless in writing signed by the parties. (e) <u>Severability</u>. If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff, Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) <u>Definitions</u>. As used herein, "<u>including</u>" means "including without limitation"; and "<u>Omron Compa-</u> nies" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROP-ERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

- Programmable Products. Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof. <u>Performance Data</u>. Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitabil-ity and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application require-2 3 ments. Actual performance is subject to the Omron's Warranty and Limitations of Liability.
- Change in Specifications. Product specifications and accessories may be 4 Change in specifications. Product specifications and accessions may be changed at any time based on improvements and other reasons. It is our prac-tice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifica-tions of the Product may be changed without any notice. When in doubt, spe-cial part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual creating of purphased Product to confirm actual specifications of purchased Product. Errors and Omissions. Information presented by Omron Companies has been
- 5 checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.



#### OMRON AUTOMATION AND SAFETY • THE AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE México DF • 52.55.59.01.43.00 • 01-800-226-6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO · SALES OFFICE Apodaca, N.L. · 52.81.11.56.99.20 · 01-800-226-6766 · mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br OMRON ARGENTINA • SALES OFFICE Cono Sur • 54.11.4783.5300

**OMRON CHILE • SALES OFFICE** Santiago • 56.9.9917.3920

OTHER OMRON LATIN AMERICA SALES 54.11.4783.5300

OMRON EUROPE B.V. • Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. • +31 (0) 23 568 13 00 • www.industrial.omron.eu

Authorized Distributor:

#### **Automation Control Systems**

- Machine Automation Controllers (MAC) 
   Programmable Controllers (PLC)
- Operator interfaces (HMI) 
   Distributed I/O 
   Software

#### **Drives & Motion Controls**

- Servo & AC Drives 
   Motion Controllers & Encoders
- **Temperature & Process Controllers**
- Single and Multi-loop Controllers

#### **Sensors & Vision**

- Proximity Sensors 
   Photoelectric Sensors 
   Fiber-Optic Sensors
- Amplified Photomicrosensors 
   Measurement Sensors
- Ultrasonic Sensors 
   Vision Sensors

#### Industrial Components

- RFID/Code Readers 
   Relays 
   Pushbuttons & Indicators
- Limit and Basic Switches 
   Timers 
   Counters 
   Metering Devices
- Power Supplies

#### Safety

• Laser Scanners • Safety Mats • Edges and Bumpers • Programmable Safety Controllers • Light Curtains • Safety Relays • Safety Interlock Switches

CSM\_E3Z\_DS\_E\_18\_1 11/14 Note: Specifications are subject to change. © 2015 Omron Electronics LLC