

5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters



FEATURES

- Patent protected
- Optimised bipolar output voltages for IGBT/ SiC & MOSFET gate drives
- Reinforced insulation to UL62368 recognition pending
- ANSI/AAMI ES60601-1 recognition pending
- 5.7kVDC isolation test voltage 'Hi Pot Test'
- Ultra low isolation capacitance
- Surface mount package style
- 5V, 12V & 15V inputs
- +15V/-9V, +15V/-5V & +20V/-5V outputs
- Operation up to 100°C (with derating)
- Short circuit protection
- Characterised CMTI >200kV/µS
- Continuous barrier withstand voltage 2.5kV
- Characterised partial discharge performance

| SELECTION GUIDE | | | | | | | | | | |
|-----------------------------|--------------------------|------------------|------------------|------------------|------------------|--------------------------------|-----------------------|---------------------------|-----------------------|------------------------|
| Order Code ¹ | Nominal Input Voltage | Output Voltage 1 | Output Voltage 2 | Output Current 1 | Output Current 2 | Input Current at Rated Load | Load Regulation (Typ) | Load Regulation The (Max) | Load Regulation (Typ) | Load Regulation ひ(Max) |
| | V | V | V | mA | | | | 9 | 6 | |
| MGJ2D051505MPC | 5 | 15 | -5 | 100 | 100 | 540 | 8 | 10 | 6 | 9 |
| MGJ2D051509MPC | 5 | 15 | -9 | 80 | 80 | 540 | 7 | 11 | 6.5 | 10 |
| MGJ2D052005MPC ⁴ | 5 | 20 | -5 | 80 | 80 | 500 | | 10 | | 9 |
| MGJ2D121505MPC | 12 | 15 | -5 | 100 | 100 | 210 | 9 | 14 | 7 | 12 |
| MGJ2D121509MPC | 12 | 15 | -9 | 80 | 80 | 210 | 8 | 13 | 7 | 12 |
| MGJ2D122005MPC ⁴ | 12 | 20 | -5 | 80 | 80 | 250 | | 12 | | 7 |
| MGJ2D151505MPC | 15 | 15 | -5 | 100 | 100 | 170 | 7 | 11 | 5.5 | 9 |
| MGJ2D151509MPC | 15 | 15 | -9 | 80 | 80 | 170 | 6 | 10 | 5 | 9 |
| MGJ2D152005MPC ⁴ | 15 | 20 | -5 | 80 | 80 | 200 | | 8 | | 7 |

| SELECTION GUIDE (| (Continued) | | | | | | |
|-----------------------------|--------------------------------------|--------------------------|------------------|------------------|--------------------------|--------------|-------|
| Order Code ¹ | Ripple & Noise (Typ) ³ | Ripple & Noise (Max)³ | Efficiency (Min) | Efficiency (Typ) | Isolation Capacitance | nF MIL. Tel. | |
| | mV | n-n | 0 | 6 | pF | | |
| | | FF | , | | P. | kH | Irs |
| MGJ2D051505MPC | 25 | 45 | 68 | 72.5 | 3 | 1362 | 13487 |
| MGJ2D051509MPC | 20 | 45 | 69 | 73 | 3 | 1221 | 12733 |
| MGJ2D052005MPC ⁴ | | 50 | 64 | 71 | 3 | | |
| MGJ2D121505MPC | 35 | 55 | 73 | 77 | 3 | 1411 | 52799 |
| MGJ2D121509MPC | 20 | 45 | 72 | 77 | 3 | 1548 | 47759 |
| MGJ2D122005MPC ⁴ | | 50 | 69 | 76 | 3 | | |
| MGJ2D151505MPC | 30 | 65 | 72 | 77 | 3 | 1224 | 56429 |
| MGJ2D151509MPC | 20 | 45 | 73 | 77 | 3 | 1332 | 56879 |
| MGJ2D152005MPC4 | | 50 | 71 | 76 | 3 | | |

| INPUT CHARACTERISTICS | | | | | | |
|---|---------------------------------------|------|------|------|-------|--|
| Parameter | Parameter Conditions | | Тур. | Max. | Units | |
| | Continuous operation, 5V input types | 4.5 | 5 | 5.5 | V | |
| Voltage range | Continuous operation, 12V input types | 10.8 | 12 | 13.2 | | |
| | Continuous operation, 15V input types | 13.5 | 15 | 16.5 | | |
| Input short circuit current I _{sc} | 5V input types | | 100 | | | |
| | 12V input types | | 90 | | mA | |
| | 15V input types | | 55 | | | |
| Input reflected ripple | 5V input type | | 10 | | mA | |
| | All others | | 5 | | p-p | |

PRODUCT OVERVIEW

The MGJ2 series of DC-DC converters is ideal for powering 'high side' and 'low side' gate drive circuits for IGBTs/SiC and MOSFETs in bridge circuits. A choice of asymmetric output voltages allows optimum drive levels for best system efficiency. The MGJ2 series is characterised for high isolation requirements commonly seen in bridge circuits used in motor drives and inverters, while the MGJ2 industrial grade temperature rating and construction gives long service life and reliability.







- 1. Components are supplied in tape and reel packaging, please refer to package specification section. Orderable part numbers are MGJ2D051505MPC-R7 (80 pieces per reel), or MGJ2D051505MPC-R13 (400 pieces per reel).
- 2. Calculated using MIL-HDBK-217 FN2 and Telcordia SR-332 calculation model with nominal input voltage at full load.
- 3. See ripple & noise test method.
- 4. MGJ2Dxx2005MPC variants are in preliminary stages.

All specifications typical at T_A=25°C, nominal input voltage and rated output current unless otherwise specified



| OUTPUT CHARACTERISTICS | | | | | |
|-------------------------------|-------------------------------|------|------|------|-------|
| Parameter | Conditions | Min. | Тур. | Max. | Units |
| Rated Power | T _A =-40°C to 85°C | | | 2.0 | W |
| Voltage Set Point Accuracy | See tolerance envelopes | | | | |
| Line regulation | 5V input types | | 1.05 | 1.1 | |
| | MGJ2D121505MPC | | 1.1 | 1.25 | |
| | MGJ2D121509MPC | | 1.1 | 1.3 | %/% |
| | 15V input types | | 1.1 | 1.2 | |
| | All others | | | | |

| ISOLATION CHARACTERISTICS | | | | | | | |
|------------------------------|----------------------|-----------------------------------|------------------------------|------|------|-------|-----|
| Parameter | Parameter Conditions | | Min. | Тур. | Max. | Units | |
| IndePendentalian | | Production tested for 1 second | | 5700 | | | VDC |
| Isolation test voltage | | Qualification tested for 1 minute | | | | | VDC |
| Resistance | | Viso= 1000VDC | | 1 | | | GΩ |
| Continuous barrier w | ithstand voltage | Non-safety barrier application | | | | 2000 | V |
| Cofety standard UL62368-1 | | Reinforced | Creepage and clearance 9mm | | | 250 | VAC |
| Safety standard ¹ | ANSI/AAMI ES60601-1 | 2 MOPP | Creepage and clearance simin | | | 250 | VAC |

| GENERAL CHARACTERISTICS | | | | | |
|-------------------------|---------------|------|------|------|-------|
| Parameter | Conditions | Min. | Тур. | Max. | Units |
| | 5V input type | | 85 | | |
| Custohing from tong | 12 input type | | 110 | | kHz |
| Switching frequency | 151505 | | 100 | | КПZ |
| | 151509 | | 90 | | |

| TEMPERATURE CHARACTERISTICS | | | | | |
|-----------------------------------|--|------|------|------|-------|
| Parameter | Conditions | Min. | Тур. | Max. | Units |
| Specification | All output types (see derating curves) | -40 | | 100 | |
| Storage | | -40 | | 125 | |
| Product Temperature above ambient | 5V input types | | 35 | | °C |
| | 12V input types | | 27 | | |
| | 15V input types | | 25 | | |
| Cooling | Free air convection | | | | |

| ABSOLUTE MAXIMUM RATINGS | | | | |
|---|------------|--|--|--|
| Short-circuit protection | Continuous | | | |
| Input voltage V _{IN} , MGJ2D05 | 6V | | | |
| Input voltage V _{IN} , MGJ2D12 | 15V | | | |
| Input voltage V _{IN} , MGJ2D15 | 18V | | | |

^{1.} UL62368-1 and ANSI/AAMI ES60601-1 recognition is currently pending.



5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

TECHNICAL NOTES

ISOLATION VOLTAGE

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions MGJ2 series of DC-DC converters are all 100% production tested at 5.7kVDC for 1 second and have been qualification tested at 5.7kVDC for 1 minute.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

When the insulation in the MGJ2 series is not used as a safety barrier, i.e. provides functional isolation only, continuous or switched voltages across the barrier up to 2.5kV are sustainable. Long term reliability testing at these voltages continues. Peak Inception voltages measured were in excess of 2.5kV when testing for partial discharge in accordance with IEC 60270. Please contact Murata for further information.

The MGJ2 series is pending recognition by Underwriters Laboratory to 250VAC Reinforced Insulation, please see safety approval section below.

REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

SAFETY APPROVAL

ANSI/AAMI ES60601-1

The MGJ2 series is pending recognition by Underwriters Laboratory (UL) to ANSI/AAMI ES60601-1 and provides 2 MOPP (Means Of Patient Protection) based upon a working voltage of 250VAC max, between Primary and Secondary.

UL62368-1

The MGJ2 series is pending recognition by Underwriters Laboratory (UL) to UL62368-1 for reinforced insulation to a working voltage of 250VAC.

Creepage and clearance 9mm.

Working altitude 5000m


ROHS COMPLIANCE AND MSL INFORMATION



This series is compatible with Pb-Free soldering systems and is also backward compatible with Sn/Pb soldering systems. The series can be soldered in accordance with J-STD-020. Please refer to <u>application notes</u> for further information. This series have a classification temperature of 260°C and moisture sensitivity level 2. The termination finish on this product is Gold with plating thickness 0.12 microns.



| ENVIRONMENTAL V | ALIDATION TESTING | | | | |
|--|--|--|--|--|--|
| The following tests have been conducted on this product series, as part of our design verification process. The datasheet characteristics specify user operating conditions for this series, please contact Murata if further information about the tests is required. | | | | | |
| Test | Standard | Condition | | | |
| Temperature cycling | JEDEC JESD22-A104 | 500 cycles in a dual zone chamber from -40 (+5/-10) $^{\circ}$ C to 105 (+10/-5) $^{\circ}$ C. 15mins dwell at each (inclusive of ramps). 2 cycles per hour. | | | |
| Humidity (unbiased) | JEDEC JESD22-A101 | 85±2°C, 85±5% R.H. for 1000 (+168/-24) hours | | | |
| Storage life | JEDEC JESD22-A103, Condition A | 125°C +10/-0°C for ≥1000 hours | | | |
| Vibration | BS EN 61373 with respect to BS EN 60068-2-64, Test Fh Category 1 Class B | $5-150$ Hz. Level at each axis – Vertical, Traverse and Longitudinal: 5.72 m/s 2 rms. 5 hours in each axis. Crest factor: 3 Sigma. Device is secured via the pads. | | | |
| Shock | BS EN 61373: 2010 Category 1, Class B | Test is 30ms duration, 3 shocks in each sense of 3 mutually perpendicular axes (18 shocks total). Level at each axis: Vertical, Traverse and Longitudinal: 50m/s2. Device is secured via the pads. | | | |
| Solderability | Based on EIA/IPC/JEDEC J-STD-002, Test B1 | For lead free solderability the parts are conditioned in a dry bake for 4 hours \pm 15 min. at a temperature of 155°C. Dipped in solder at 245°C \pm 5°C for 7-10 seconds. | | | |
| Solvent cleaning | Resistance to cleaning agents | Solvent – Novec 71IPA & Topklean EL-20A. Pulsed ultrasonic immersion 45°C- 65°C | | | |
| Solvent resistance | MIL-STD-883 Method 2015 | The parts and the bristle portion of the brush are immersed in Isopropanol for a minimum of 1 minute. The parts are brushed 3 times, after the third time the parts are blown dry and inspected. | | | |



5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters


CHARACTERISATION TEST METHODS

Ripple & Noise Characterisation Method

Ripple and noise measurements are performed with the following test configuration.

| C1 | 1μF X7R multilayer ceramic capacitor, voltage rating to be a minimum of 3 times the output voltage of the DC-DC converter | | | |
|-------------|--|--|--|--|
| C2 | $10\mu F$ tantalum capacitor, voltage rating to be a minimum of 1.5 times the output voltage of the DC-DC converter with an ESR of less than $100 \text{m}\Omega$ at 100 kHz | | | |
| C3 | 100nF multilayer ceramic capacitor, general purpose | | | |
| R1 | 450Ω resistor, carbon film, ±1% tolerance | | | |
| R2 | 50Ω BNC termination | | | |
| T1 | 3T of the coax cable through a ferrite toroid | | | |
| RLOAD | Resistive load to the maximum power rating of the DC-DC converter. Connections should be made via twisted wires | | | |
| Measured va | ues are multiplied by 10 to obtain the specified values. | | | |

Differential Mode Noise Test Schematic



APPLICATION NOTES

Minimum load

The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically 1.25 times the specified output voltage if the output load falls to less than 5%.


Gate Drive Applications Advisory Note

For general guidance for product usage in gate drive applications please refer to "gate drive application notes".

Capacitive loading and start up

| | Start-up time |
|----------------|---------------|
| | ms |
| | 10μF |
| MGJ2D051505MPC | 5 |
| MGJ2D051509MPC | 6 |
| MGJ2D052005MPC | |
| MGJ2D121505MPC | 3 |
| MGJ2D121509MPC | 4 |
| MGJ2D122005MPC | |
| MGJ2D151505MPC | 3 |
| MGJ2D151509MPC | 4 |
| MGJ2D152005MPC | |

Typical Start-Up Wave Form






5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

APPLICATION NOTES (Continued)


The MGJ2 series is a dual output DC-DC specifically designed for gate drive applications and its output configuration is not suitable for application usage as a general dual output DC-DC converter. However the MGJ2 series can be used as a general purpose single output converter, by loading from +Vout to -Vout.

The MGJ2 series provides a dual output by using a patented pnp emitter follower current shunt divider network circuit with short circuit protection.




Optional Configuration:


For optional configuration where alternative negative output voltages are required, an external zener diode network can be connected across the main 20V or 24V output. However this zener diode will no longer be protected from short circuits as the internal short circuit protection is bypassed.















5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

POSITIVE OUTPUT VOLTAGE TOLERANCE ENVELOPES (continued)


The voltage tolerance envelopes show typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading and set point accuracy.





MGJ2D152005MPC









5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters




The voltage tolerance envelopes show typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading and set point accuracy.






MGJ2D152005MPC



















5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

EMC FILTERING AND SPECTRA The following filter circuit and filter table shows the input filters typically required to meet EN55022 Quasi-PeakCurve A or B. DC C1 = C2 Cdamp = DC **Cdamp** Electrolytic capacitor Inductor Capacitor C1&2, µF L1, μΗ SMD Through Hole Part number Cdamp, µF MGJ2D051505MPC 84223C 10 GRM188C81C106MA73 22 11R223C 100 GRM188C81C106MA73 MGJ2D051509MPC 22 84223C 11R223C 10 100 MGJ2D052005MPC MGJ2D121505MPC 84223C 11R223C GRM188C81C106MA73 100 22 10 MGJ2D121509MPC 84223C 11R223C 10 GRM188C81C106MA73 100 22 MGJ2D122005MPC MGJ2D151505MPC 33 84333C 11R333C 10 GRM188C81C106MA73 100 MGJ2D151509MPC 84333C 11R333C 10 GRM188C81C106MA73 100 MGJ2D152005MPC MGJ2D051505MPC (Average) 80 80 70 70 60 60 50 50 dBuV dBuV 40 40 30 30 20 20 10 O 1.00E+05 1.00E+06 1.00E+07 1.00E+08 1.00E+05 1.00E+08 1.00E+06 1.00E+07 Frequency (Hz) Frequency (Hz) MGJ2D051509MPC (Average) MGJ2D051509MPC (Quasi-Peak) 80 80 70 70 60 60

50

40

30

20

10

1.00E+05

1.00E+06

Frequency (Hz)

1.00E+07

dBuV

1.00E+08

50

40

30

20

10

1.00E+05

1.00E+06


Frequency (Hz)

1.00E+07


dBuV

1.00E+08
















5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

TAPE & REEL SPECIFICATIONS Reel Outline Dimensions Reel Packaging Details Ø330 OR Ø178 ø 13.5 12.8 LEADER SECTION 400 MIN 38.4 MAX# 100 0 MIN 0 MIN ## W GOODS **ENCLOSURE** SECTION 0 TRAILER SECTION 160 MIN Tape & Reel specifications shall conform with current EIA-481 standard Unless otherwise stated all dimensions in mm (inches) Controlling dimension is mm # Measured at hub ## Six equi-spaced slots on 180mm/7" reel Reel Quantity: 7" - 80 or 13" - 400 Tape Outline Dimensions 4.0 32.0 28.4 COVER TAPE 15.5# Tape & Reel specifications shall conform with current EIA-481 standard 24.0 Unless otherwise stated all dimensions in mm

Components shall be orientated within the carrier tape as indicated # Measured on a plane 0.3mm above the bottom pocket



5.7kVDC Isolated 2W SM Gate Drive DC-DC Converters

DISCLAIMER

Unless otherwise stated in the datasheet, all products are designed for standard commercial and industrial applications and NOT for safety-critical and/or life-critical applications.

Particularly for safety-critical and/or life-critical applications, i.e. applications that may directly endanger or cause the loss of life, inflict bodily harm and/or loss or severe damage to equipment/property, and severely harm the environment, a prior explicit written approval from Murata is strictly required. Any use of Murata standard products for any safety-critical, life-critical or any related applications without any prior explicit written approval from Murata shall be deemed unauthorised use.

These applications include but are not limited to:

- Aircraft equipment
- Aerospace equipment
- Undersea equipment
- Power plant control equipment
- Medical equipment
- Transportation equipment (automobiles, trains, ships, etc.)
- Traffic signal equipment
- Disaster prevention / crime prevention equipment
- Data Processing equipment

Murata makes no express or implied warranty, representation, or guarantee of suitability, fitness for any particular use/purpose and/or compatibility with any application or device of the buyer, nor does Murata assume any liability whatsoever arising out of unauthorised use of any Murata product for the application of the buyer. The suitability, fitness for any particular use/purpose and/or compatibility of Murata product with any application or device of the buyer remain to be the responsibility and liability of the buyer.

Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm, and take appropriate remedial actions. Buyer will fully indemnify and hold Murata, its affiliated companies, and its representatives harmless against any damages arising out of unauthorised use of any Murata products in any safety-critical and/or life-critical applications.

Remark: Murata in this section refers to Murata Manufacturing Company and its affiliated companies worldwide including, but not limited to, Murata Power Solutions.



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>:

Refer to: https://www.murata.com/en-eu/products/power/requirements

Murata Power Solution(Milton keynes) Ltd. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein don timply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are suffered to change without notice.

2021 Murata Power Solution(Milton keynes) Ltd.