INTEGRATED CIRCUITS

DATA SHEET

For a complete data sheet, please also download:

• The IC06 74HC/HCT/HCU/HCMOS Logic Family Specifications

74HC/HCT4066Quad bilateral switches

Product specification Supersedes data of 1998 Oct 02 File under Integrated Circuits, IC06 1998 Nov 10





Quad bilateral switches

74HC/HCT4066

FEATURES

• Very low "ON" resistance:

50 Ω (typ.) at $V_{CC} = 4.5 \text{ V}$

45 Ω (typ.) at $V_{CC} = 6.0 \text{ V}$

35 Ω (typ.) at V_{CC} = 9.0 V

· Output capability: non-standard

• I_{CC} category: SSI.

The 74HC/HCT4066 have four independent analog switches. Each switch has two input/output terminals (nY, nZ) and an active HIGH enable input (nE). When nE is LOW the belonging analog switch is turned off.

The "4066" is pin compatible with the "4016" but exhibits a much lower "ON" resistance. In addition, the "ON" resistance is relatively constant over the full input signal range.

GENERAL DESCRIPTION

The 74HC/HCT4066 are high-speed Si-gate CMOS devices and are pin compatible with the "4066" of the "4000B" series. They are specified in compliance with JEDEC standard no. 7A.

QUICK REFERENCE DATA

 $GND = 0 V; T_{amb} = 25 °C; t_r = t_f = 6 ns$

SYMBOL	PARAMETER	CONDITIONS	TYP	UNIT		
STIVIBUL	PARAWEIER	CONDITIONS	нс	нст	ONII	
t _{PZH} / t _{PZL}	turn-on time nE to V _{os}	$C_L = 15 \text{ pF}; R_L = 1 \text{ k}\Omega; V_{CC} = 5 \text{ V}$	11	12	ns	
t _{PHZ} / t _{PLZ}	turn-off time nE to Vos		13	16	ns	
C _I	input capacitance		3.5	3.5	pF	
C _{PD}	power dissipation capacitance per switch	notes 1 and 2	11	12	pF	
Cs	max. switch capacitance		8	8	pF	

Notes

- 1. C_{PD} is used to determine the dynamic power dissipation (P_D in μW):
 - a) $P_D = C_{PD} \times V_{CC}^2 \times f_i + \sum \{(C_L + C_S) \times V_{CC}^2 \times f_o\}$ where:
 - b) f_i = input frequency in MHz
 - c) f_o = output frequency in MHz
 - d) $\sum \{(C_L + C_S) \times V_{CC}^2 \times f_0\} = \text{sum of outputs}$
 - e) C_L = output load capacitance in pF
 - f) $C_S = \text{maximum switch capacitance in pF}$
 - g) V_{CC} = supply voltage in V
- 2. For HC the condition is V_I = GND to V_{CC} For HCT the condition is V_I = GND to V_{CC} – 1.5 V

Quad bilateral switches


74HC/HCT4066


ORDERING INFORMATION

TYPE		PACKAGE	
NUMBER	NAME	DESCRIPTION	VERSION
74HC4066	DIP14	plastic dual in-line package; 14 leads (300 mil)	SOT27-1
74HC4066	SO14	plastic small outline package; 14 leads; body width 3.9 mm	SOT108-1
74HC4066	SSOP14	plastic shrink small outline package; 14 leads; body width 5.3 mm	SOT337-1
74HC4066	TSSOP14	plastic thin shrink small outline package; 14 leads; body width 4.4 mm	SOT402-1
74HCT4066	DIP14	plastic dual in-line package; 14 leads (300 mil)	SOT27-1
74HCT4066	SO14	plastic small outline package; 14 leads; body width 3.9 mm	SOT108-1
74HCT4066	SSOP14	plastic shrink small outline package; 14 leads; body width 5.3 mm	SOT337-1
74HCT4066	TSSOP14	plastic thin shrink small outline package; 14 leads; body width 4.4 mm	SOT402-1

PIN DESCRIPTION


PIN NO.	SYMBOL	NAME AND FUNCTION
1, 4, 8, 11	1Y to 4Y	independent inputs/outputs
2, 3, 9, 10	1Z to 4Z	independent inputs/outputs
7	GND	ground (0 V)
13, 5, 6, 12	1E to 4E	enable inputs (active HIGH)
14	V _{CC}	positive supply voltage






Quad bilateral switches

74HC/HCT4066






FUNCTION TABLE

INPUT NE	SWITCH
L	off
Н	on

Note

1. H = HIGH voltage level; L = LOW voltage level.



Quad bilateral switches

74HC/HCT4066

RATINGS

Limiting values in accordance with the Absolute Maximum System (IEC 134) Voltages are referenced to GND (GND = 0 V)

SYMBOL	PARAMETER	MIN.	MAX.	UNIT	CONDITIONS
V _{CC}	DC supply voltage	-0.5	+11.0	V	
±I _{IK}	DC digital input diode current		20	mA	for $V_I < -0.5 \text{ V}$ or $V_I > V_{CC} + 0.5 \text{ V}$
±I _{SK}	DC switch diode current		20	mA	for $V_S < -0.5 \text{ V}$ or $V_S > V_{CC} + 0.5 \text{ V}$
±I _{IS}	DC switch current		25	mA	for -0.5 V < V _S < V _{CC} + 0.5 V
±I _{CC;} ±I _{GND}	DC V _{CC} or GND current		50	mA	
T _{stg}	storage temperature range	-65	+150	°C	
P _{tot}	power dissipation per package				for temperature range: -40 to +125 °C 74HC/HCT
	plastic DIL		750	mW	above +70 °C: derate linearly with 12 mW/K
	plastic mini-pack (SO)		500	mW	above +70 °C: derate linearly with 8 mW/K
Ps	power dissipation per switch		100	mW	

Note

To avoid drawing V_{CC} current out of terminal nZ, when switch current flows in terminal nY, the voltage drop across
the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal nZ, no V_{CC} current will flow
out of terminal nY. In this case there is no limit for the voltage drop across the switch, but the voltages at nY and nZ
may not exceed V_{CC} or GND.

RECOMMENDED OPERATING CONDITIONS

CVMDOL	PARAMETER		74HC			74HC1	Γ	UNIT	CONDITIONS
SYMBOL	PARAIVIETER	min.	typ.	max.	min.	typ.	max.	UNII	CONDITIONS
V _{CC}	DC supply voltage	2.0	5.0	10.0	4.5	5.0	5.5	٧	
VI	DC input voltage range	GND		V _{CC}	GND		V _{CC}	V	
Vs	DC switch voltage range	GND		V _{CC}	GND		Vcc	٧	
T _{amb}	operating ambient temperature range	-40		+85	-40		+85	°C	see DC and AC CHARACTERISTICS
T _{amb}	operating ambient temperature range	-40		+125	-40		+125	°C	
t _r , t _f	input rise and fall times		6.0	1000		6.0	500	ns	V _{CC} = 2.0 V
				500					V _{CC} = 4.5 V
				400					V _{CC} = 6.0 V
				250					V _{CC} = 10.0 V

Quad bilateral switches

74HC/HCT4066

DC CHARACTERISTICS FOR 74HC/HCT

For 74HC: V_{CC} = 2.0, 4.5, 6.0 and 9.0 V; For 74HCT: V_{CC} = 4.5 V


				•	Γ _{amb} (°	C)				TE	TEST CONDITIONS				
SYMBOL	PARAMETER		74HC/HCT												
STIVIBUL		+25			-40 to +85 -40 t			+125	UNIT	V _{CC}	l _S (μ A)	V _{IS}	Vı		
		min.	typ.	max.	min.	max.	min.	max.		(-,	(102.1)				
R _{ON}	ON-resistance (peak)		_	_		_		_	Ω	2.0	100	V _{CC}	V_{IH}		
			54	95		118		142	Ω	4.5	1000	to	or		
		42	84		105		126	Ω	6.0	1000	GND	V_{IL}			
			32	70		88		105	Ω	9.0	1000				
R _{ON}	ON-resistance (rail)		80	_		_		_	Ω	2.0	100	GND	V_{IH}		
			35	75		95		115	Ω	4.5	1000		or		
			27	65		82		100	Ω	6.0	1000		V_{IL}		
			20	55		70		85	Ω	9.0	1000				
R _{ON}	ON-resistance (rail)		100	-		_		_	Ω	2.0	100	V _{CC}	V_{IH}		
			42	80		106		128	Ω	4.5	1000		or		
			35	75		94		113	Ω	6.0	1000		V_{IL}		
			27	60		78		95	Ω	9.0	1000				
ΔR_{ON}	maximum variation of		_						Ω	2.0		V_{CC}	V_{IH}		
	ON-resistance between		5						Ω	4.5		to	or		
а	any two channels		4						Ω	6.0		GND \	V_{IL}		
			3						Ω	9.0					


Note


^{1.} At supply voltages approaching 2 V, the analog switch ON-resistance becomes extremely non-linear. Therefore it is recommended that these devices be used to transmit digital signals only, when using these supply voltages.

Quad bilateral switches

74HC/HCT4066








Quad bilateral switches

74HC/HCT4066



Quad bilateral switches

74HC/HCT4066

DC CHARACTERISTICS FOR 74HC

Voltage are referenced to GND (ground = 0 V)

	PARAMETER			•	T _{amb} (°C	C)					TEST (CONDITIONS
		74HC										
SYMBOL		+25			-40 to	-40 to +85		−40 to +125		V _{CC} (V)	VI	OTHER
		min.	typ.	max.	min.	max.	min.	max				
V _{IH}	HIGH-level input	1.5	1.2		1.5		1.5		V	2.0		
	voltage	3.15	2.4		3.15		3.15			4.5		
		4.2	3.2		4.2		4.2			6.0		
		6.3	4.7		6.3		6.3			9.0		
V_{IL}	LOW-level input		0.8	0.50		0.50		0.50	V	2.0		
	voltage		2.1	1.35		1.35		1.35		4.5		
			2.8	1.80		1.80		1.80		6.0		
			4.3	2.70		2.70		2.70		9.0		
±I _I	input leakage			0.1		1.0		1.0	μΑ	6.0	V _{CC}	
	current			0.2		2.0		2.0		10.0	or GND	
±I _S	analog switch OFF-state current per channel			0.1		1.0		1.0	μΑ	10.0	V _{IH} or V _{IL}	$V_S = V_{CC} - GND$ (see Fig.7)
±I _S	analog switch ON-state current			0.1		1.0		1.0	μΑ	10.0	V _{IH} or V _{IL}	$V_S = V_{CC} - GND$ (see Fig.8)
I _{CC}	quiescent supply current			2.0 4.0		20.0 40.0		40.0 80.0	μΑ	6.0	V _{CC} or GND	$V_{is} = GND \text{ or } V_{CC};$ $V_{os} = V_{CC} \text{ or } GND$

Quad bilateral switches

74HC/HCT4066

AC CHARACTERISTICS FOR 74HC

 $GND = 0 \ V; \ t_r = t_f = 6 \ ns; \ C_L = 50 \ pF$

		T _{amb} (°C)								TE	ST CONDITIONS
CVMDOL	DADAMETED		74HC								OTHER
SYMBOL	PARAMETER	+25			-40 to +85			-40 to +125		V _{CC}	OTHER
		min.	typ.	max.	min.	max.	min.	max.		(',	
t _{PHL} /t _{PLH}	propagation delay		8	60		75		90	ns	2.0	R _L = ∞;
	V _{is} to V _{os}		3	12		15		18		4.5	$C_L = 50 \text{ pF}$
			2	10		13		15		6.0	(see Fig.18)
			2	8		10		12		9.0	
t _{PZH} /t _{PZL}	turn-on time		36	100		125		150	ns	2.0	$R_L = 1 \text{ k}\Omega;$
	nE to V _{os}		13	20		25		30		4.5	$C_L = 50 \text{ pF}$
			10	17		21		26		6.0	(see Figs 19 and 20)
			8	13		16		20		9.0	and 20)
t _{PHZ} /t _{PLZ}	turn-off time		44	150		190		225	ns	2.0	$R_L = 1 \text{ k}\Omega;$
	nE to V _{os}		16	30		38		45		4.5	$C_L = 50 \text{ pF}$
			13	26		33		38		6.0	(see Figs 19 and 20)
			16	24		16		20		9.0	una 20)

Quad bilateral switches

74HC/HCT4066

DC CHARACTERISTICS FOR 74HCT

Voltages are referenced to GND (ground = 0 V)

				•	T _{amb} (°	°C)		TEST CONDITIONS				
SYMBOL	PARAMETER	74HCT							UNIT			
STIVIBUL		+25			-40 to +85		-40 to +125		UNIT	V _{CC}	VI	OTHER
		min.	typ.	max.	min.	max.	min.	max.		(,		
V _{IH}	HIGH-level input voltage	2.0	1.6		2.0		2.0		V	4.5 to 5.5		
V _{IL}	LOW-level input voltage		1.2	0.8		0.8		0.8	V	4.5 to 5.5		
±l ₁	input leakage current			0.1		1.0		1.0	μΑ	5.5	V _{CC} or GND	
±Is	analog switch OFF-state current per channel			0.1		1.0		1.0	μΑ	5.5	V _{IH} or V _{IL}	$V_S = V_{CC} - GND$ (see Fig.7)
±I _S	analog switch ON-state current			0.1		1.0		1.0	μΑ	5.5	V _{IH} or V _{IL}	$V_S = V_{CC} - GND$ (see Fig.8)
Icc	quiescent supply current			2.0		20.0		40.0	μΑ	4.5 to 5.5	V _{CC} or GND	$V_{is} = GND \text{ or}$ $V_{CC}; V_{os} = V_{CC} \text{ or}$ GND
Δl _{CC}	additional quiescent supply current per input pin for unit load coefficient is 1 (note 1)		100	360		450		490	μΑ	4.5 to 5.5	V _{CC} – 2.1 V	other inputs at V _{CC} or GND

Note

Table 1

INPUT	UNIT LOAD COEFFICIENT
nE	1.00

^{1.} The value of additional quiescent supply current (ΔI_{CC}) for a unit load of 1 is given here. To determine ΔI_{CC} per input, multiply this value by the unit load coefficient shown in the table below.

Quad bilateral switches

74HC/HCT4066

AC CHARACTERISTICS FOR 74HCT

 $GND = 0 V; t_r = t_f = 6 ns$

	DADAMETER		T _{amb} (°C) 74HCT								TEST CONDITIONS		
SYMBOL											OTHER		
STIMBUL	PARAMETER		+25		-40 t	to +85	-40 to	+125	UNIT	V _{CC}	OTHER		
		min.	typ.	max.	min.	max.	min.	max.		(-,			
t _{PHL} /t _{PLH}	propagation delay V _{is} to V _{os}		3	12		15		18	ns	4.5	$R_L = \infty$; $C_L = 50 \text{ pF}$ (see Fig.18)		
t _{PZH} /t _{PZL}	turn-on time nE to V _{os}		12	24		30		36	ns	4.5	$R_L = 1 \text{ k}\Omega; C_L = 50 \text{ pF}$ (see Figs 19 and 20)		
t _{PHZ} /t _{PLZ}	turn-off time nE to V _{os}		20	35		44		53	ns	4.5	$R_L = 1 \text{ k}\Omega; C_L = 50 \text{ pF}$ (see Figs 19 and 20)		

ADDITIONAL AC CHARACTERISTICS FOR 74HC/HCT

Recommended conditions and typical values GND = 0 V; $t_r = t_f = 6$ ns


SYMBOL	PARAMETER	TYP.	UNIT	V _{CC} (V)	V _{IS(p-p)} (V)	CONDITIONS
	sine wave distortion f = 1 kHz	0.04	%	4.5	4.0	$R_L = 10 \text{ k}\Omega; C_L = 50 \text{ pF}$
		0.02	%	9.0	8.0	(see Fig.16)
	sine wave distortion f = 10 kHz	0.12	%	4.5	4.0	$R_L = 10 \text{ k}\Omega; C_L = 50 \text{ pF}$
		0.06	%	9.0	8.0	(see Fig.16)
	switch "OFF" signal feed-through	-50	dB	4.5	note 3	$R_L = 600 \Omega; C_L = 50 pF;$
		-50	dB	9.0		f = 1 MHz (see Figs 10 and 17)
	crosstalk between any two	-60	dB	4.5	note 3	$R_L = 600 \Omega; C_L = 50 pF;$
	switches	-60	dB	9.0		f = 1 MHz (see Fig.12)
V _(p-p)	crosstalk voltage between enable	110	mV	4.5		$R_L = 600 \Omega; C_L = 50 pF;$
	or address input to any switch (peak-to-peak value)	220	mV	9.0		f = 1 MHz (nE, square wave between V_{CC} and GND, $t_r = t_f = 6$ ns) (see Fig.14)
f _{max}	minimum frequency response	180	MHz	4.5	note 4	$R_L = 50 \Omega; C_L = 10 pF$
	(–3 dB)	200	MHz	9.0		(see Figs 11 and 15)
Cs	maximum switch capacitance	8	pF			


Notes

- 1. V_{is} is the input voltage at nY or nZ terminal, whichever is assigned as an input.
- 2. V_{os} is the output voltage at nY or nZ terminal, whichever is assigned as an output.
- 3. Adjust input voltage V_{is} is 0 dBM level (0 dBM = 1 mW into 600 Ω).
- 4. Adjust input voltage V_{is} is 0 dBM level at V_{os} for 1 MHz (0 dBM = 1 mW into 50 Ω).

Quad bilateral switches

74HC/HCT4066





Quad bilateral switches

74HC/HCT4066




Fig.12 Test circuit for measuring crosstalk between any two switches; channel ON condition.






Fig.13 Test circuit for measuring crosstalk between any two switches; channel OFF condition.




Quad bilateral switches


74HC/HCT4066



Adjust input voltage to obtain 0 dBM at V_{os} when f_{in} = 1 MHz. After set-up frequency of f_{in} is increased to obtain a reading of -3 dB at V_{os} .

Fig.15 Test circuit for measuring minimum frequency response.







Quad bilateral switches


74HC/HCT4066

AC WAVEFORMS





TEST CIRCUIT AND WAVEFORMS



Quad bilateral switches

74HC/HCT4066

Table 2 Conditions

TEST	SWITCH	V _{IS}
t _{PZH}	GND	V _{CC}
t _{PZL}	V _{CC}	GND
t _{PHZ}	GND	V _{CC}
t _{PLZ}	V _{CC}	GND
others	open	pulse

 Table 3
 Definitions for Figs 20 and 21:

SYMBOL DEFINITION

 $\begin{array}{ll} C_L & \mbox{load capacitance including jig and probe capacitance (see AC CHARACTERISTICS for values)} \\ R_T & \mbox{termination resistance should be equal to the output impedance Z_O of the pulse generator} \\ t_r & \mbox{t}_f = 6 \ \mbox{ns}, \ \mbox{when measuring f_{max}, there is no constraint on t_r, t_f with 50% duty factor} \\ \end{array}$




Table 4

			t _r ; t _f				
FAMILY	AMPLITUDE	V _M	f _{max} ; PULSE WIDTH	OTHER			
74HC	V _{CC}	50%	< 2 ns	6 ns			
74HCT	3.0 V	1.3 V	< 2 ns	6 ns			


Quad bilateral switches

74HC/HCT4066

PACKAGE OUTLINES

DIP14: plastic dual in-line package; 14 leads (300 mil)

SOT27-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

ı	UNIT	A max.	A ₁ min.	A ₂ max.	b	b ₁	С	D ⁽¹⁾	E ⁽¹⁾	e	e ₁	L	ME	Мн	w	Z ⁽¹⁾ max.
	mm	4.2	0.51	3.2	1.73 1.13	0.53 0.38	0.36 0.23	19.50 18.55	6.48 6.20	2.54	7.62	3.60 3.05	8.25 7.80	10.0 8.3	0.254	2.2
ir	nches	0.17	0.020	0.13	0.068 0.044	0.021 0.015	0.014 0.009	0.77 0.73	0.26 0.24	0.10	0.30	0.14 0.12	0.32 0.31	0.39 0.33	0.01	0.087

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.


OUTLINE		REFER	ENCES	EUROPEAN	ISSUE DATE
VERSION	IEC	JEDEC	EIAJ	PROJECTION	1330E DATE
SOT27-1	050G04	MO-001AA			92-11-17 95-03-11

Quad bilateral switches

74HC/HCT4066

SO14: plastic small outline package; 14 leads; body width 3.9 mm

SOT108-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	Q	v	w	у	z ⁽¹⁾	θ
mm	1.75	0.25 0.10	1.45 1.25	0.25	0.49 0.36	0.25 0.19	8.75 8.55	4.0 3.8	1.27	6.2 5.8	1.05	1.0 0.4	0.7 0.6	0.25	0.25	0.1	0.7 0.3	8°
inches	0.069	0.010 0.004	0.057 0.049	0.01		0.0100 0.0075	0.35 0.34	0.16 0.15	0.050	0.244 0.228	0.041	0.039 0.016	0.028 0.024	0.01	0.01	0.004	0.028 0.012	0°

Note

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.


OUTLINE				EUROPEAN	ISSUE DATE
VERSION	IEC	JEDEC	EIAJ	PROJECTION	ISSUE DATE
SOT108-1	076E06S	MS-012AB			95-01-23 97-05-22

Quad bilateral switches

74HC/HCT4066

SSOP14: plastic shrink small outline package; 14 leads; body width 5.3 mm

SOT337-1



						Ψ,												
UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽¹⁾	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	2.0	0.21 0.05	1.80 1.65	0.25	0.38 0.25	0.20 0.09	6.4 6.0	5.4 5.2	0.65	7.9 7.6	1.25	1.03 0.63	0.9 0.7	0.2	0.13	0.1	1.4 0.9	8° 0°

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.


OUTLINE		REFER	ENCES	EUROPEAN	ISSUE DATE
VERSION	IEC	JEDEC	EIAJ	PROJECTION	ISSUE DATE
SOT337-1		MO-150AB			-95-02-04 96-01-18

Quad bilateral switches

74HC/HCT4066

TSSOP14: plastic thin shrink small outline package; 14 leads; body width 4.4 mm

SOT402-1



D	.0.10 (u. o	09	iiiai aiii		,												
UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽²⁾	е	HE	L	Lp	Q	v	w	у	Z ⁽¹⁾	θ
mm	1.10	0.15 0.05	0.95 0.80	0.25	0.30 0.19	0.2 0.1	5.1 4.9	4.5 4.3	0.65	6.6 6.2	1.0	0.75 0.50	0.4 0.3	0.2	0.13	0.1	0.72 0.38	8° 0°

Notes

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFER	ENCES	EUROPEAN	ISSUE DATE
VERSION	IEC	JEDEC	EIAJ	PROJECTION	ISSUE DATE
SOT402-1		MO-153			94-07-12 95-04-04

Quad bilateral switches

74HC/HCT4066

SOLDERING

Introduction

This text gives a very brief insight to a complex technology. A more in-depth account of soldering ICs can be found in our "Data Handbook IC26; Integrated Circuit Packages" (document order number 9398 652 90011).

There is no soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and surface mount components are mixed on one printed-circuit board. However, wave soldering is not always suitable for surface mount ICs, or for printed-circuit boards with high population densities. In these situations reflow soldering is often used.

Through-hole mount packages

SOLDERING BY DIPPING OR BY SOLDER WAVE

The maximum permissible temperature of the solder is 260 °C; solder at this temperature must not be in contact with the joints for more than 5 seconds. The total contact time of successive solder waves must not exceed 5 seconds.

The device may be mounted up to the seating plane, but the temperature of the plastic body must not exceed the specified maximum storage temperature ($T_{stg(max)}$). If the printed-circuit board has been pre-heated, forced cooling may be necessary immediately after soldering to keep the temperature within the permissible limit.

MANUAL SOLDERING

Apply the soldering iron (24 V or less) to the lead(s) of the package, either below the seating plane or not more than 2 mm above it. If the temperature of the soldering iron bit is less than 300 °C it may remain in contact for up to 10 seconds. If the bit temperature is between 300 and 400 °C, contact may be up to 5 seconds.

Surface mount packages

REFLOW SOLDERING

Reflow soldering requires solder paste (a suspension of fine solder particles, flux and binding agent) to be applied to the printed-circuit board by screen printing, stencilling or pressure-syringe dispensing before package placement.

Several methods exist for reflowing; for example, infrared/convection heating in a conveyor type oven. Throughput times (preheating, soldering and cooling) vary between 100 and 200 seconds depending on heating method.

Typical reflow peak temperatures range from 215 to 250 °C. The top-surface temperature of the packages should preferable be kept below 230 °C.

WAVE SOLDERING

Conventional single wave soldering is not recommended for surface mount devices (SMDs) or printed-circuit boards with a high component density, as solder bridging and non-wetting can present major problems.

To overcome these problems the double-wave soldering method was specifically developed.

If wave soldering is used the following conditions must be observed for optimal results:

- Use a double-wave soldering method comprising a turbulent wave with high upward pressure followed by a smooth laminar wave.
- For packages with leads on two sides and a pitch (e):
 - larger than or equal to 1.27 mm, the footprint longitudinal axis is **preferred** to be parallel to the transport direction of the printed-circuit board;
 - smaller than 1.27 mm, the footprint longitudinal axis must be parallel to the transport direction of the printed-circuit board.

The footprint must incorporate solder thieves at the downstream end.

 For packages with leads on four sides, the footprint must be placed at a 45° angle to the transport direction of the printed-circuit board. The footprint must incorporate solder thieves downstream and at the side corners.

During placement and before soldering, the package must be fixed with a droplet of adhesive. The adhesive can be applied by screen printing, pin transfer or syringe dispensing. The package can be soldered after the adhesive is cured.

Typical dwell time is 4 seconds at 250 °C. A mildly-activated flux will eliminate the need for removal of corrosive residues in most applications.

MANUAL SOLDERING

Fix the component by first soldering two diagonally-opposite end leads. Use a low voltage (24 V or less) soldering iron applied to the flat part of the lead. Contact time must be limited to 10 seconds at up to $300\ ^{\circ}$ C.

When using a dedicated tool, all other leads can be soldered in one operation within 2 to 5 seconds between 270 and 320 $^{\circ}$ C.

Quad bilateral switches

74HC/HCT4066

Suitability of IC packages for wave, reflow and dipping soldering methods

MOUNTING	PACKAGE	SOLDERING METHOD					
MOUNTING	PACKAGE	WAVE	REFLOW ⁽¹⁾	DIPPING			
Through-hole mount	DBS, DIP, HDIP, SDIP, SIL	suitable ⁽²⁾	_	suitable			
Surface mount	HLQFP, HSQFP, HSOP, SMS	not suitable ⁽³⁾	suitable	_			
	PLCC ⁽⁴⁾ , SO	suitable	suitable	_			
	LQFP, QFP, TQFP	not recommended ⁽⁴⁾⁽⁵⁾	suitable	_			
	SQFP	not suitable	suitable	_			
	SSOP, TSSOP, VSO	not recommended ⁽⁶⁾	suitable	_			

Notes

- 1. All surface mount (SMD) packages are moisture sensitive. Depending upon the moisture content, the maximum temperature (with respect to time) and body size of the package, there is a risk that internal or external package cracks may occur due to vaporization of the moisture in them (the so called popcorn effect). For details, refer to the Drypack information in the "Data Handbook IC26; Integrated Circuit Packages; Section: Packing Methods".
- 2. For SDIP packages, the longitudinal axis must be parallel to the transport direction of the printed-circuit board.
- 3. These packages are not suitable for wave soldering as a solder joint between the printed-circuit board and heatsink (at bottom version) can not be achieved, and as solder may stick to the heatsink (on top version).
- 4. If wave soldering is considered, then the package must be placed at a 45° angle to the solder wave direction. The package footprint must incorporate solder thieves downstream and at the side corners.
- 5. Wave soldering is only suitable for LQFP, QFP and TQFP packages with a pitch (e) equal to or larger than 0.8 mm; it is definitely not suitable for packages with a pitch (e) equal to or smaller than 0.65 mm.
- 6. Wave soldering is only suitable for SSOP and TSSOP packages with a pitch (e) equal to or larger than 0.65 mm; it is definitely not suitable for packages with a pitch (e) equal to or smaller than 0.5 mm.

DEFINITIONS

Data sheet status	
Objective specification	This data sheet contains target or goal specifications for product development.
Preliminary specification	This data sheet contains preliminary data; supplementary data may be published later.
Product specification	This data sheet contains final product specifications.
Limiting values	

Limiting values

Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information

Where application information is given, it is advisory and does not form part of the specification.

LIFE SUPPORT APPLICATIONS

These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips for any damages resulting from such improper use or sale.

Philips Semiconductors – a worldwide company

Argentina: see South America

Australia: 34 Waterloo Road, NORTH RYDE, NSW 2113,

Tel. +61 2 9805 4455, Fax. +61 2 9805 4466

Austria: Computerstr. 6, A-1101 WIEN, P.O. Box 213, Tel. +43 160 1010,

Fax. +43 160 101 1210

Belarus: Hotel Minsk Business Center, Bld. 3, r. 1211, Volodarski Str. 6,

220050 MINSK, Tel. +375 172 200 733, Fax. +375 172 200 773

Belgium: see The Netherlands Brazil: see South America

Bulgaria: Philips Bulgaria Ltd., Energoproject, 15th floor,

51 James Bourchier Blvd., 1407 SOFIA, Tel. +359 2 689 211, Fax. +359 2 689 102

Canada: PHILIPS SEMICONDUCTORS/COMPONENTS,

Tel. +1 800 234 7381

China/Hong Kong: 501 Hong Kong Industrial Technology Centre,

72 Tat Chee Avenue, Kowloon Tong, HONG KONG,

Tel. +852 2319 7888, Fax. +852 2319 7700

Colombia: see South America Czech Republic: see Austria

Denmark: Prags Boulevard 80, PB 1919, DK-2300 COPENHAGEN S,

Tel. +45 32 88 2636, Fax. +45 31 57 0044 Finland: Sinikalliontie 3, FIN-02630 ESPOO, Tel. +358 9 615800, Fax. +358 9 61580920

France: 51 Rue Carnot, BP317, 92156 SURESNES Cedex,

Tel. +33 1 40 99 6161, Fax. +33 1 40 99 6427

Germany: Hammerbrookstraße 69, D-20097 HAMBURG,

Tel. +49 40 23 53 60, Fax. +49 40 23 536 300

Greece: No. 15, 25th March Street, GR 17778 TAVROS/ATHENS,

Tel. +30 1 4894 339/239, Fax. +30 1 4814 240

Hungary: see Austria

India: Philips INDIA Ltd, Band Box Building, 2nd floor, 254-D, Dr. Annie Besant Road, Worli, MUMBAI 400 025,

Tel. +91 22 493 8541, Fax. +91 22 493 0966

Indonesia: PT Philips Development Corporation, Semiconductors Division,

Gedung Philips, Jl. Buncit Raya Kav.99-100, JAKARTA 12510, Tel. +62 21 794 0040 ext. 2501, Fax. +62 21 794 0080

Ireland: Newstead, Clonskeagh, DUBLIN 14 Tel. +353 1 7640 000, Fax. +353 1 7640 200

Israel: RAPAC Electronics, 7 Kehilat Saloniki St, PO Box 18053, TEL AVIV 61180, Tel. +972 3 645 0444, Fax. +972 3 649 1007

Italy: PHILIPS SEMICONDUCTORS, Piazza IV Novembre 3, 20124 MILANO, Tel. +39 2 6752 2531, Fax. +39 2 6752 2557

Japan: Philips Bldg 13-37, Kohnan 2-chome, Minato-ku, TOKYO 108-8507, Tel. +81 3 3740 5130, Fax. +81 3 3740 5077

Korea: Philips House, 260-199 Itaewon-dong, Yongsan-ku, SEOUL,

Tel. +82 2 709 1412, Fax. +82 2 709 1415

Malaysia: No. 76 Jalan Universiti, 46200 PETALING JAYA, SELANGOR,

Tel. +60 3 750 5214, Fax. +60 3 757 4880

Mexico: 5900 Gateway East, Suite 200, EL PASO, TEXAS 79905,

Tel. +9-5 800 234 7381

Middle East: see Italy

Netherlands: Postbus 90050, 5600 PB EINDHOVEN, Bldg. VB,

Tel. +31 40 27 82785, Fax. +31 40 27 88399

New Zealand: 2 Wagener Place, C.P.O. Box 1041, AUCKLAND,

Tel. +64 9 849 4160, Fax. +64 9 849 7811 Norway: Box 1, Manglerud 0612, OSLO, Tel. +47 22 74 8000, Fax. +47 22 74 8341

Pakistan: see Singapore

Philippines: Philips Semiconductors Philippines Inc., 106 Valero St. Salcedo Village, P.O. Box 2108 MCC, MAKATI, Metro MANILA, Tel. +63 2 816 6380, Fax. +63 2 817 3474

Poland: UI. Lukiska 10, PL 04-123 WARSZAWA, Tel. +48 22 612 2831, Fax. +48 22 612 2327

Portugal: see Spain Romania: see Italy

Russia: Philips Russia, UI. Usatcheva 35A, 119048 MOSCOW,

Tel. +7 095 755 6918, Fax. +7 095 755 6919

Singapore: Lorong 1, Toa Payoh, SINGAPORE 319762,

Tel. +65 350 2538, Fax. +65 251 6500

Slovakia: see Austria Slovenia: see Italy

South Africa: S.A. PHILIPS Pty Ltd., 195-215 Main Road Martindale,

2092 JOHANNESBURG, P.O. Box 7430 Johannesburg 2000,

Tel. +27 11 470 5911, Fax. +27 11 470 5494 South America: Al. Vicente Pinzon, 173, 6th floor,

04547-130 SÃO PAULO, SP, Brazil, Tel. +55 11 821 2333, Fax. +55 11 821 2382

Spain: Balmes 22, 08007 BARCELONA Tel. +34 93 301 6312, Fax. +34 93 301 4107

Sweden: Kottbygatan 7, Akalla, S-16485 STOCKHOLM,

Tel. +46 8 5985 2000, Fax. +46 8 5985 2745 Switzerland: Allmendstrasse 140, CH-8027 ZÜRICH,

Tel. +41 1 488 2741 Fax. +41 1 488 3263 Taiwan: Philips Semiconductors, 6F, No. 96, Chien Kuo N. Rd., Sec. 1,

TAIPEI, Taiwan Tel. +886 2 2134 2865, Fax. +886 2 2134 2874

Thailand: PHILIPS ELECTRONICS (THAILAND) Ltd.

209/2 Sanpavuth-Bangna Road Prakanong, BANGKOK 10260, Tel. +66 2 745 4090, Fax. +66 2 398 0793

Turkey: Talatpasa Cad. No. 5, 80640 GÜLTEPE/ISTANBUL,

Tel. +90 212 279 2770. Fax. +90 212 282 6707

Ukraine: PHILIPS UKRAINE, 4 Patrice Lumumba str., Building B, Floor 7,

252042 KIEV, Tel. +380 44 264 2776, Fax. +380 44 268 0461

United Kingdom: Philips Semiconductors Ltd., 276 Bath Road, Hayes, MIDDLESEX UB3 5BX, Tel. +44 181 730 5000, Fax. +44 181 754 8421

United States: 811 East Arques Avenue, SUNNYVALE, CA 94088-3409,

Tel. +1 800 234 7381

Uruguay: see South America Vietnam: see Singapore

Yugoslavia: PHILIPS, Trg N. Pasica 5/v, 11000 BEOGRAD,

Tel. +381 11 625 344, Fax.+381 11 635 777

For all other countries apply to: Philips Semiconductors, International Marketing & Sales Communications, Building BE-p, P.O. Box 218, 5600 MD EINDHOVEN, The Netherlands, Fax. +31 40 27 24825

© Philips Electronics N.V. 1998

SCA60

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

245106/00/03/pp24

Date of release: 1998 Nov 10

Document order number: 9397 750 04779

Let's make things better.

Internet: http://www.semiconductors.philips.com





