Welding Proximity Sensor E2EW Series DC 3-wire

Stable detection in lines containing both aluminum and iron

- Equivalent sensing distances for both iron and aluminum ¹
- Enables common design for lines with both iron and aluminum ¹
- The exceptional sensing range ², which means fewer false detections and thereby fewer unexpected stoppages.
- OMRON's unique fluororesin coating technologies enable longlasting spatter resistance ⁴, eliminates the need to replace for 10 years ³.
- Durable full metal body to reduce unexpected downtime
- 2-output (NO+NC) models and models with IO-Link ¹ are also available.
- Laser printed information (sensing distance on the sensor head, model on the cable, and model on the metal part of the connector model) reduce errors during sensor replacement. ⁵
- Weld field immunity cancels pulse noise from magnetic fields. ¹
- UL certification (UL60947-5-2) and
- CSA certification (CSA C22.2 UL60947-5-2-14)
- PREMIUM Models only.
 Based on November 2020 OMRON investigation.
- Based on November 2020 OWNON investigation.
 This value assumes that the sensor operates 10 hours a day in an arc welding environment and is cleaned once a month (12 times a year).
 If our previous model (E2EF-Q) needs to be replaced once every 3 times it is cleaned, the E2EW-Q Proximity Sensor needs to be replaced once every 180 times it is cleaned. This means that there is no need to replace the E2EW-Q Proximity Sensor for 10 or more years.
- 4. Models with spatter-resistant coating only.
- 5. Models without spatter-resistant coating only.

E2EW Series Model Number Legend

DC 3-wire



No.	Туре	Code	Meaning	
(1)	Casa	Blank	Without spatter-resistant coating	
(1)	Case	Q	With spatter-resistant coating	
(2)	Sensing distance	Number	Sensing distance (Unit: mm)	
(2)	Outeut configuration	В	PNP open collector	
(3)	Output configuration	С	NPN open collector	
		1	Normally open (NO)	
(4)	Operation mode	2	Normally closed (NC)	
		3	Normally open, Normally closed (NO+NC)	
		Blank	Non IO-Link compliant	
(5)	IO-Link baud rate	D	COM2 (38.4kbps)	
		Т	COM3 (230.4kbps)	
		12	M12	
(6)	Size	18	M18	
		30	M30	
		Blank	Pre-wired Models	
(7)	Connection method	M1	M12 Connector Models	
		M1TJ	M12 Pre-wired Smartclick Connector Models	
(8)	Cable length	Number M	Cable length	

Note: The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number. Models are not available for all combinations of code numbers.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Ordering Information

PREMIUM Model

E2EW Series (Quadruple distance model)

DC 3-wire [Refer to Dimensions on page 26.]

Shielded ¹

Size	Connection method	Operation mode	Model		
ensing distance)	Connection method	Operation mode	PNP	NPN	
		NO	E2EW-X7B1T12 2M	E2EW-X7C112 2M	
	Pre-wired (2 m) ²	NC	E2EW-X7B212 2M	E2EW-X7C212 2M	
		NO+NC	E2EW-X7B3T12 2M	E2EW-X7C312 2M	
		NO	E2EW-X7B1T12-M1TJ 0.3M	E2EW-X7C112-M1TJ 0.3M	
M12 (7 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X7B212-M1TJ 0.3M	E2EW-X7C212-M1TJ 0.3M	
(, ,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		NO+NC	E2EW-X7B3T12-M1TJ 0.3M	E2EW-X7C312-M1TJ 0.3M	
		NO	E2EW-X7B1T12-M1	E2EW-X7C112-M1	
	M12 Connector	NC	E2EW-X7B212-M1	E2EW-X7C212-M1	
		NO+NC	E2EW-X7B3T12-M1	E2EW-X7C312-M1	
		NO	E2EW-X12B1T18 2M	E2EW-X12C118 2M	
	Pre-wired (2 m) ²	NC	E2EW-X12B218 2M	E2EW-X12C218 2M	
		NO+NC	E2EW-X12B3T18 2M	E2EW-X12C318 2M	
		NO	E2EW-X12B1T18-M1TJ 0.3M	E2EW-X12C118-M1TJ 0.3M	
M18 (12 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X12B218-M1TJ 0.3M	E2EW-X12C218-M1TJ 0.3M	
(12 1111)		NO+NC	E2EW-X12B3T18-M1TJ 0.3M	E2EW-X12C318-M1TJ 0.3M	
		NO	E2EW-X12B1T18-M1	E2EW-X12C118-M1	
	M12 Connector	NC	E2EW-X12B218-M1	E2EW-X12C218-M1	
		NO+NC	E2EW-X12B3T18-M1	E2EW-X12C318-M1	
		NO	E2EW-X22B1T30 2M	E2EW-X22C130 2M	
	Pre-wired (2 m) ²	NC	E2EW-X22B230 2M	E2EW-X22C230 2M	
		NO+NC	E2EW-X22B3T30 2M	E2EW-X22C330 2M	
		NO	E2EW-X22B1T30-M1TJ 0.3M	E2EW-X22C130-M1TJ 0.3M	
M30 (22 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X22B230-M1TJ 0.3M	E2EW-X22C230-M1TJ 0.3M	
(NO+NC	E2EW-X22B3T30-M1TJ 0.3M	E2EW-X22C330-M1TJ 0.3M	
		NO	E2EW-X22B1T30-M1	E2EW-X22C130-M1	
	M12 Connector	NC	E2EW-X22B230-M1	E2EW-X22C230-M1	
		NO+NC	E2EW-X22B3T30-M1	E2EW-X22C330-M1	

1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 24.

2. Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-X7B1T12 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM3). For IO-Link (COM2), select a model number with the format of "E2EW-X□□□□" (Example: E2EW-X7B1D12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

PREMIUM Model

E2EW Series (Triple distance model)

DC 3-wire [Refer to *Dimensions* on page 26.] Shielded ¹

Size	Connection method	Operation mode	Model		
ensing distance)	Connection method	Operation mode	PNP	NPN	
		NO	E2EW-X6B1T12 2M	E2EW-X6C112 2M	
	Pre-wired (2 m) ²	NC	E2EW-X6B212 2M	E2EW-X6C212 2M	
		NO+NC	E2EW-X6B3T12 2M	E2EW-X6C312 2M	
		NO	E2EW-X6B1T12-M1TJ 0.3M	E2EW-X6C112-M1TJ 0.3M	
M12 (6 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X6B212-M1TJ 0.3M	E2EW-X6C212-M1TJ 0.3M	
(0 1111)		NO+NC	E2EW-X6B3T12-M1TJ 0.3M	E2EW-X6C312-M1TJ 0.3M	
		NO	E2EW-X6B1T12-M1	E2EW-X6C112-M1	
	M12 Connector	NC	E2EW-X6B212-M1	E2EW-X6C212-M1	
		NO+NC	E2EW-X6B3T12-M1	E2EW-X6C312-M1	
		NO	E2EW-X10B1T18 2M	E2EW-X10C118 2M	
	Pre-wired (2 m) ²	NC	E2EW-X10B218 2M	E2EW-X10C218 2M	
		NO+NC	E2EW-X10B3T18 2M	E2EW-X10C318 2M	
	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-X10B1T18-M1TJ 0.3M	E2EW-X10C118-M1TJ 0.3M	
M18 (10 mm)		NC	E2EW-X10B218-M1TJ 0.3M	E2EW-X10C218-M1TJ 0.3M	
(101111)		NO+NC	E2EW-X10B3T18-M1TJ 0.3M	E2EW-X10C318-M1TJ 0.3M	
		NO	E2EW-X10B1T18-M1	E2EW-X10C118-M1	
	M12 Connector	NC	E2EW-X10B218-M1	E2EW-X10C218-M1	
		NO+NC	E2EW-X10B3T18-M1	E2EW-X10C318-M1	
		NO	E2EW-X20B1T30 2M	E2EW-X20C130 2M	
	Pre-wired (2 m) ²	NC	E2EW-X20B230 2M	E2EW-X20C230 2M	
		NO+NC	E2EW-X20B3T30 2M	E2EW-X20C330 2M	
		NO	E2EW-X20B1T30-M1TJ 0.3M	E2EW-X20C130-M1TJ 0.3M	
M30 (20 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X20B230-M1TJ 0.3M	E2EW-X20C230-M1TJ 0.3M	
(20 mm)		NO+NC	E2EW-X20B3T30-M1TJ 0.3M	E2EW-X20C330-M1TJ 0.3M	
		NO	E2EW-X20B1T30-M1	E2EW-X20C130-M1	
	M12 Connector	NC	E2EW-X20B230-M1	E2EW-X20C230-M1	
		NO+NC	E2EW-X20B3T30-M1	E2EW-X20C330-M1	

1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 24.

2. Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-X6B1T12 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM3). For IO-Link (COM2), select a model number with the format of "E2EW-X□□D□" (Example: E2EW-X6B1D12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

PREMIUM Model

E2EW-Q Series (Spatter-resistant Quadruple distance model)

DC 3-wire [Refer to *Dimensions* on page 26.] Shielded ¹

Size	Connection method	Operation mode	Model		
Sensing distance)	Connection method	Operation mode	PNP	NPN	
		NO	E2EW-QX7B1T12 2M	E2EW-QX7C112 2M	
	Pre-wired (2 m) ²	NC	E2EW-QX7B212 2M	E2EW-QX7C212 2M	
		NO+NC	E2EW-QX7B3T12 2M	E2EW-QX7C312 2M	
		NO	E2EW-QX7B1T12-M1TJ 0.3M	E2EW-QX7C112-M1TJ 0.3M	
M12 (7 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX7B212-M1TJ 0.3M	E2EW-QX7C212-M1TJ 0.3M	
(, ,,,,,)		NO+NC	E2EW-QX7B3T12-M1TJ 0.3M	E2EW-QX7C312-M1TJ 0.3M	
		NO	E2EW-QX7B1T12-M1	E2EW-QX7C112-M1	
	M12 Connector	NC	E2EW-QX7B212-M1	E2EW-QX7C212-M1	
		NO+NC	E2EW-QX7B3T12-M1	E2EW-QX7C312-M1	
		NO	E2EW-QX12B1T18 2M	E2EW-QX12C118 2M	
	Pre-wired (2 m) ²	NC	E2EW-QX12B218 2M	E2EW-QX12C218 2M	
		NO+NC	E2EW-QX12B3T18 2M	E2EW-QX12C318 2M	
		NO	E2EW-QX12B1T18-M1TJ 0.3M	E2EW-QX12C118-M1TJ 0.3M	
M18 (12 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX12B218-M1TJ 0.3M	E2EW-QX12C218-M1TJ 0.3M	
(-=)		NO+NC	E2EW-QX12B3T18-M1TJ 0.3M	E2EW-QX12C318-M1TJ 0.3M	
		NO	E2EW-QX12B1T18-M1	E2EW-QX12C118-M1	
	M12 Connector	NC	E2EW-QX12B218-M1	E2EW-QX12C218-M1	
		NO+NC	E2EW-QX12B3T18-M1	E2EW-QX12C318-M1	
		NO	E2EW-QX22B1T30 2M	E2EW-QX22C130 2M	
	Pre-wired (2 m) ²	NC	E2EW-QX22B230 2M	E2EW-QX22C230 2M	
		NO+NC	E2EW-QX22B3T30 2M	E2EW-QX22C330 2M	
		NO	E2EW-QX22B1T30-M1TJ 0.3M	E2EW-QX22C130-M1TJ 0.3M	
M30 (22 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX22B230-M1TJ 0.3M	E2EW-QX22C230-M1TJ 0.3M	
(22 1111)		NO+NC	E2EW-QX22B3T30-M1TJ 0.3M	E2EW-QX22C330-M1TJ 0.3M	
		NO	E2EW-QX22B1T30-M1	E2EW-QX22C130-M1	
	M12 Connector	NC	E2EW-QX22B230-M1	E2EW-QX22C230-M1	
		NO+NC	E2EW-QX22B3T30-M1	E2EW-QX22C330-M1	

1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 24.

2. Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-QX7B1T12 5M)

Note: 1. Models in ______ are equipped with IO-Link (COM3). For IO-Link (COM2), select a model number with the format of "E2EW-QXIIIIDI" (Example: E2EW-QX7B1D12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

PREMIUM Model

E2EW-Q Series (Spatter-resistant Triple distance model)

DC 3-wire [Refer to *Dimensions* on page 26.] Shielded ¹

Size	Connection method	Operation mode	Model		
ensing distance)	Connection method	Operation mode	PNP	NPN	
		NO	E2EW-QX6B1T12 2M	E2EW-QX6C112 2M	
	Pre-wired (2 m) ²	NC	E2EW-QX6B212 2M	E2EW-QX6C212 2M	
		NO+NC	E2EW-QX6B3T12 2M	E2EW-QX6C312 2M	
		NO	E2EW-QX6B1T12-M1TJ 0.3M	E2EW-QX6C112-M1TJ 0.3M	
M12 (6 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX6B212-M1TJ 0.3M	E2EW-QX6C212-M1TJ 0.3M	
(0 1111)		NO+NC	E2EW-QX6B3T12-M1TJ 0.3M	E2EW-QX6C312-M1TJ 0.3M	
		NO	E2EW-QX6B1T12-M1	E2EW-QX6C112-M1	
	M12 Connector	NC	E2EW-QX6B212-M1	E2EW-QX6C212-M1	
		NO+NC	E2EW-QX6B3T12-M1	E2EW-QX6C312-M1	
		NO	E2EW-QX10B1T18 2M	E2EW-QX10C118 2M	
	Pre-wired (2 m) ²	NC	E2EW-QX10B218 2M	E2EW-QX10C218 2M	
		NO+NC	E2EW-QX10B3T18 2M	E2EW-QX10C318 2M	
		NO	E2EW-QX10B1T18-M1TJ 0.3M	E2EW-QX10C118-M1TJ 0.3M	
M18 (10 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX10B218-M1TJ 0.3M	E2EW-QX10C218-M1TJ 0.3M	
(101111)		NO+NC	E2EW-QX10B3T18-M1TJ 0.3M	E2EW-QX10C318-M1TJ 0.3M	
		NO	E2EW-QX10B1T18-M1	E2EW-QX10C118-M1	
	M12 Connector	NC	E2EW-QX10B218-M1	E2EW-QX10C218-M1	
		NO+NC	E2EW-QX10B3T18-M1	E2EW-QX10C318-M1	
		NO	E2EW-QX20B1T30 2M	E2EW-QX20C130 2M	
	Pre-wired (2 m) ²	NC	E2EW-QX20B230 2M	E2EW-QX20C230 2M	
		NO+NC	E2EW-QX20B3T30 2M	E2EW-QX20C330 2M	
		NO	E2EW-QX20B1T30-M1TJ 0.3M	E2EW-QX20C130-M1TJ 0.3M	
M30 (20 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX20B230-M1TJ 0.3M	E2EW-QX20C230-M1TJ 0.3M	
(=0 1111)		NO+NC	E2EW-QX20B3T30-M1TJ 0.3M	E2EW-QX20C330-M1TJ 0.3M	
		NO	E2EW-QX20B1T30-M1	E2EW-QX20C130-M1	
	M12 Connector	NC	E2EW-QX20B230-M1	E2EW-QX20C230-M1	
		NO+NC	E2EW-QX20B3T30-M1	E2EW-QX20C330-M1	

1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 24.

2. Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-QX6B1T12 5M)

Operation mode NO can be changed to NC via IO-Link communications.

BASIC Model

E2EW Series (Single distance model)

DC 3-wire [Refer to *Dimensions* on page 27.] Shielded

Size	Connection method	Operation mode	Model		
(Sensing distance)	Connection method	Operation mode	PNP	NPN	
		NO	E2EW-X2B112 2M	E2EW-X2C112 2M	
	Pre-wired (2 m) *	NC	E2EW-X2B212 2M	E2EW-X2C212 2M	
M12		NO+NC	E2EW-X2B312 2M	E2EW-X2C312 2M	
(2 mm)		NO	E2EW-X2B112-M1TJ 0.3M	E2EW-X2C112-M1TJ 0.3M	
	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X2B212-M1TJ 0.3M	E2EW-X2C212-M1TJ 0.3M	
		NO+NC	E2EW-X2B312-M1TJ 0.3M	E2EW-X2C312-M1TJ 0.3M	
		NO	E2EW-X5B118 2M	E2EW-X5C118 2M	
	Pre-wired (2 m) *	NC	E2EW-X5B218 2M	E2EW-X5C218 2M	
M18		NO+NC	E2EW-X5B318 2M	E2EW-X5C318 2M	
(5 mm)		NO	E2EW-X5B118-M1TJ 0.3M	E2EW-X5C118-M1TJ 0.3M	
	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X5B218-M1TJ 0.3M	E2EW-X5C218-M1TJ 0.3M	
		NO+NC	E2EW-X5B318-M1TJ 0.3M	E2EW-X5C318-M1TJ 0.3M	
		NO	E2EW-X10B130 2M	E2EW-X10C130 2M	
	Pre-wired (2 m) *	NC	E2EW-X10B230 2M	E2EW-X10C230 2M	
M30		NO+NC	E2EW-X10B330 2M	E2EW-X10C330 2M	
(10 mm)		NO	E2EW-X10B130-M1TJ 0.3M	E2EW-X10C130-M1TJ 0.3M	
	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-X10B230-M1TJ 0.3M	E2EW-X10C230-M1TJ 0.3M	
		NO+NC	E2EW-X10B330-M1TJ 0.3M	E2EW-X10C330-M1TJ 0.3M	

* Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-X2B112 5M)

Note: IO-Link is not supported for all types of BASIC Model.

BASIC Model

E2EW-Q Series (Spatter-resistant Single distance model)

DC 3-wire [Refer to Dimensions on page 27.] Shielded

Size	Connection method	Operation mode	Model		
(Sensing distance)	Connection method	Operation mode	PNP	NPN	
		NO	E2EW-QX2B112 2M	E2EW-QX2C112 2M	
	Pre-wired (2 m) *	NC	E2EW-QX2B212 2M	E2EW-QX2C212 2M	
M12		NO+NC	E2EW-QX2B312 2M	E2EW-QX2C312 2M	
(2 mm)		NO	E2EW-QX2B112-M1TJ 0.3M	E2EW-QX2C112-M1TJ 0.3M	
	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX2B212-M1TJ 0.3M	E2EW-QX2C212-M1TJ 0.3M	
		NO+NC	E2EW-QX2B312-M1TJ 0.3M	E2EW-QX2C312-M1TJ 0.3M	
		NO	E2EW-QX5B118 2M	E2EW-QX5C118 2M	
	Pre-wired (2 m) *	NC	E2EW-QX5B218 2M	E2EW-QX5C218 2M	
M18		NO+NC	E2EW-QX5B318 2M	E2EW-QX5C318 2M	
(5 mm)		NO	E2EW-QX5B118-M1TJ 0.3M	E2EW-QX5C118-M1TJ 0.3M	
	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX5B218-M1TJ 0.3M	E2EW-QX5C218-M1TJ 0.3M	
		NO+NC	E2EW-QX5B318-M1TJ 0.3M	E2EW-QX5C318-M1TJ 0.3M	
		NO	E2EW-QX10B130 2M	E2EW-QX10C130 2M	
	Pre-wired (2 m) *	NC	E2EW-QX10B230 2M	E2EW-QX10C230 2M	
M30		NO+NC	E2EW-QX10B330 2M	E2EW-QX10C330 2M	
(10 mm)		NO	E2EW-QX10B130-M1TJ 0.3M	E2EW-QX10C130-M1TJ 0.3M	
	M12 Pre-wired Smartclick Connector (0.3 m)	NC	E2EW-QX10B230-M1TJ 0.3M	E2EW-QX10C230-M1TJ 0.3M	
		NO+NC	E2EW-QX10B330-M1TJ 0.3M	E2EW-QX10C330-M1TJ 0.3M	

* Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-QX2B112 5M)

Note: IO-Link is not supported for all types of BASIC Model.

Accessories (Sold Separately)

Sensor I/O Connectors

(Models for Pre-wired Connectors) A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Round Water-resistant Connectors XS2 series

Appearance	Cable Specification	Туре	Cable diameter (mm)	Cable Connection Direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
					2	XS2F-M12PVC4S2M	
				Straight	5	XS2F-M12PVC4S5M	
M12		Sockets on One	6 dia.		10	XS2F-M12PVC4S10M	
Connector		Cable End	6 dia.		2	XS2F-M12PVC4A2M	
Straight type				Right-angle	5	XS2F-M12PVC4A5M	-
otraight type					10	XS2F-M12PVC4A10M	
					1	XS2W-D421-C81-F	-
E DI					2	XS2W-D421-D81-F	E2EW-X□-M1
OF	PVC robot cable			Straight (Socket)/ Straight (Plug)	3	XS2W-D421-E81-F	E2EW-QX -M1
	PVC TODOL CADIE				5	XS2W-D421-G81-F	E2EW-X -M1TJ
						XS2W-D421-J81-F	E2EW-QX□-M1TJ
Right-angle type		Socket and Plug	C dia	Right-angle (Socket)/	2	XS2W-D422-D81-F	
		on Cable Ends	6 dia.	Right-angle (Plug)	5	XS2W-D422-G81-F	-
Chill III				Straight (Socket)/	2	XS2W-D423-D81-F	-
C				Right-angle (Plug)	5	XS2W-D423-G81-F	-
				Right-angle (Socket)/	2	XS2W-D424-D81-F	
				Straight (Plug)	5	XS2W-D424-G81-F	

Ratings and Specifications

PREMIUM Model

E2EW Series (Quadruple/Triple distance model) E2EW-Q Series (Spatter-resistant Quadruple/Triple distance model)

DC 3-wire

Shielded

	Туре	Qua	adruple distance m	odel		Friple distance mod	el			
	Size	M12	M18	M30	M12	M18	M30			
ltem	Model	E2EW-(Q)X7□12	E2EW-(Q)X12□18	E2EW-(Q)X22□30	E2EW-(Q)X6□12	E2EW-(Q)X10□18	E2EW-(Q)X20 3			
Sensing distance	9	7 mm ±10%	12 mm ±10%	22 mm ±10%	6 mm ±10%	10 mm ±10%	20 mm ±10%			
Setting distance		0 to 4.9 mm 0 to 8.4 mm 0 to 15.4 mm 0 to 4.2 mm 0 to 7.0 mm 0 to 14 mm								
Differential trave	I	15% max. of sensir	ig distance							
Detectable objec	t	Ferrous metals and Engineering Data o		(The sensing distanc	e depends on the ma	aterial of the sensing	object. Refer to			
Standard sensing	g object	Iron, 21 × 21 × 1 mm	Iron, 36 × 36 × 1 mm	Iron, 66 × 66 × 1 mm	lron, 18 × 18 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 60 × 60 × 1 mm			
Response freque	ency ¹	2 Hz								
Power supply vo	Itage	10 to 30 VDC (inclu	iding 10% ripple (p-p)), Class 2						
Current consum	ption	720 mW max. (Cur	rent consumption: 30	mA max. at power s	upply voltage of 24	/)				
Output configura	ition	B Models: PNP o	pen collector, C M	odels: NPN open col	lector					
Operation mode		1-output models (B	1, C1): NO (Normally 2, C2): NC (Normally 3, C3): NO+NC (Nor		closed)					
Control output	Load current			0 VDC, Class 2, 200 , Class 2, 100 mA m						
Control output	Residual voltage		, , , ,	x. (Load current: 200 ad current: 100 mA, 0	, 0	2 m)				
Indicator		In the IO-Link comr blinking at 1 s interv	nunication mode (CC vals)	Dperation indicator (o DM mode): Operation	indicator (orange, lit) and communication	indicator (green,			
Protection circui		Power supply reverse polarity protection, Surge suppressor, Output short-circuit protection, Output reverse polarity protection								
Ambient temperature range		Operating: 0 to 85 °C, Storage: -15 to 85 °C (with no icing or condensation) ³								
Ambient humidity range		Operating/Storage: 35% to 95% (with no condensation)								
Temperature influence		±20% max. of sensing distance at 23 °C in the temperature range of 0 to 85 °C								
Voltage influence		±1.5% max. of sensing distance at rated voltage in the rated voltage ±15% range								
nsulation resista	ance	50 M Ω min. (at 500 VDC) between current-carrying parts and case								
Dielectric strength		1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case								
Vibration resista	nce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions								
Shock resistance	e (destruction)	1,000 m/s ² 10 times each in X, Y, and Z directions								
Degree of protec	tion	IEC 60529: IP67								
Connection meth	nod	Pre-wired Models (Standard cable length: 2 m), Pre-wired Connector Models (Standard cable length: 0.3 m), M12 Connector Models								
	Pre-wired	Approx. 140 g	Approx. 165 g	Approx. 225 g	Approx. 140 g	Approx. 165 g	Approx. 225 g			
Weight (packed state)	M12 Pre-wired Smartclick Connector	Approx. 70 g	Approx. 100 g	Approx. 160 g	Approx. 70 g	Approx. 100 g	Approx. 160 g			
	M12 Connector	Approx. 60 g	Approx. 75 g	Approx. 135 g	Approx. 60 g	Approx. 75 g	Approx. 135 g			
	Case	E2EW-X : Stainle	ss steel (SUS303), E	2EW-QX : Fluorore	esin coating (Base m	aterial: (SUS303))				
	Sensing surface	E2EW-X : Stainle	ss steel (SUS303), E	2EW-QX : Fluorore	sin coating (Base m	aterial: (SUS303))				
Materials	Sensing surface (Thickness)	0.4 mm	0.4 mm	0.5 mm	0.4 mm	0.4 mm	0.5 mm			
	Clamping nuts	E2EW-X : Stainle	ss steel (SUS303), E	2EW-QX : Fluorore	esin coating (Base m	aterial: (SUS303))				
	Toothed washers	Zinc-plated iron								
	Cable	Vinyl chloride (PVC)								
Main IO-Link fun	ctions ²	Operation mode switching between NO and NC, self diagnosis enabling, excessive proximity judgment distance selecting, timer function of the control output and timer time selecting, instability output (IO-Link mode) ON delay timer time selecting function, monitor output, operating hours read-out, readout of the sensor internal temperature, and initial reset								
	IO-Link specification	Ver.1.1								
IO-Link Communication	Baud rate	E2EW(-Q) X B	Г□: COM3 (230.4 kb	ops), E2EW(-Q) X⊟B	B□D□: COM2 (38.4	kbps)				
specifications ²	Data length	PD size: 2 bytes, O	D size: 1 byte (M-se	quence type: TYPE_2	2_2)					
	Minimum cycle time	COM2: 2.3 ms, CO	M3: 1.0 ms							
Accessories		Instruction manual.	Clamping nuts, Tool	hed washer						

The response frequency is an average value. Factory setting: (timer function: ONOFF delay)
 IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.
 UL temperature rating is between 0 °C to 60 °C.

E2EW Series (Single distance model) E2EW-Q Series (Spatter-resistant Single distance model)

DC 3-wire

Shielded

	Туре		Single distance model					
	Size	M12	- M18	M30				
Item	Model	E2EW-(Q)X2□12	E2EW-(Q)X5□18	E2EW-(Q)X10□30				
Sensing distance)	2 mm ±10%	5 mm ±10%	10 mm ±10%				
Setting distance		0 to 1.4 mm	0 to 1.4 mm 0 to 3.5 mm 0 to 7 mm					
Differential trave	l	10% max. of sensing distance		<u>I</u>				
Detectable object	t	Ferrous metals and non-ferrous metal to <i>Engineering Data</i> on page 11.)	s (The sensing distance depends on th	e material of the sensing object. Ref				
Standard sensing	g object	Iron, 12 × 12 × 1 mm	Iron, 18 × 18 × 1 mm	Iron, 30 × 30 × 1 mm				
Response freque	ency ¹	100 Hz	80 Hz	40 Hz				
Power supply vo	Itage	10 to 30 VDC (including 10% ripple (p	p-p)), Class 2					
Current consump	otion	1-output models (B1, B2, C1, C2): 16 2-output models (B3, C3): 20 mA max						
Output configura	ition	B□ Models: PNP open collector, C□ Models: NPN open collector						
Operation mode		1-output models (B1, C1): NO (Norma 1-output models (B2, C2): NC (Norma 2-output models (B3, C3): NO+NC (N	ally closed),					
Control output	Load current	1-output models (B1, B2, C1, C2): 10 to 30 VDC, Class 2, 200 mA max. 2-output models (B3, C3): 10 to 30 VDC, Class 2, 100 mA max.						
Control output	Residual voltage	1-output models (B1, B2, C1, C2): 2 V max. (Load current: 200 mA, Cable length: 2 m) 2-output models (B3, C3): 2 V max. (Load current: 100 mA, Cable length: 2 m)						
Indicator		Operation indicator (orange, lit) and communication indicator (green, not lit)						
Protection circuit	ts	Power supply reverse polarity protection, Surge suppressor, Output short-circuit protection, Output reverse polarity protection						
Ambient tempera	ature range	Operating: 0 to 85 °C, Storage: -15 to 85 °C (with no icing or condensation) ²						
Ambient humidit	y range	Operating/Storage: 35% to 95% (with no condensation)						
Temperature influ	uence	±20% max. of sensing distance at 23 °C in the temperature range of 0 to 85 °C						
Voltage influence	9	±1.5% max. of sensing distance at rated voltage in the rated voltage ±15% range						
Insulation resista	ance	50 M Ω min. (at 500 VDC) between current-carrying parts and case						
Dielectric strengt	th	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case						
Vibration resista	nce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock resistance	e (destruction)	1,000 m/s ² 10 times each in X, Y, and Z directions						
Degree of protec	tion	IEC 60529: IP67						
Connection meth	nod	Pre-wired Models (Standard cable ler	ngth: 2 m), Pre-wired Connector Model	s (Standard cable length: 0.3 m)				
	Pre-wired	Approx. 140 g	Approx. 160 g	Approx. 225 g				
Weight (packed state)	M12 Pre-wired Smartclick Connector	Approx. 70 g	Approx. 95 g	Approx. 160 g				
	Case	E2EW-X : Stainless steel (SUS303)	, E2EW-QX⊡: Fluororesin coating (Ba	ase material: (SUS303))				
	Sensing surface	E2EW-X : Stainless steel (SUS303)	, E2EW-QX : Fluororesin coating (Ba	ase material: (SUS303))				
Materials	Sensing surface (Thickness)	0.8 mm	0.8 mm	0.8 mm				
	Clamping nuts	E2EW-X : Stainless steel (SUS303)	, E2EW-QX⊡: Fluororesin coating (Ba	ase material: (SUS303))				
	Toothed washers	Zinc-plated iron	0.0	. "				
	Cable	Vinyl chloride (PVC)						
Accessories		Instruction manual, Clamping nuts, To	pothed washer					
	fraguanavia an avaraga v		as follows: standard sansing ship	at a distance of twice the stand				

1. The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.


2. UL temperature rating is between 0 °C to 60 °C.


Engineering Data (Reference Value)


Sensing Area

PREMIUM Model

Quadruple distance model/ Spatter-resistant Quadruple distance model Shielded









Triple distance model/ Spatter-resistant Triple distance model Shielded

Sensing object: iron




Sensing object: Aluminum



BASIC Model

Single distance model/ Spatter-resistant Single distance model Shielded

Sensing object: iron




Influence of Sensing Object Size and Material


PREMIUM Model

Quadruple distance model/ Spatter-resistant Quadruple distance model Shielded






Size: M18 E2EW-(Q)X12□18




Size: M30 E2EW-(Q)X22□30




Triple distance model/ Spatter-resistant Triple distance model Shielded


Size: M12 E2EW-(Q)X6□12



Size: M18 E2EW-(Q)X10 18




Size: M30 E2EW-(Q)X20 30




BASIC Model

Single distance model/ Spatter-resistant Single distance model Shielded






Size: M18 E2EW-(Q)X5□18




Size: M30 E2EW-(Q)X10 30




Influence of Sensing Object Thickness and Material

PREMIUM Model


Quadruple distance model/ Spatter-resistant Quadruple distance model Shielded



Size: M18 E2EW-(Q)X12□18




Size: M30 E2EW-(Q)X22□30




Triple distance model/ Spatter-resistant Triple distance model Shielded


Size: M12 E2EW-(Q)X6□12








Size: M30 E2EW-(Q)X20 30




BASIC Model

Single distance model/ Spatter-resistant Single distance model Shielded


Size: M12 E2EW-(Q)X2□12



Size: M18 E2EW-(Q)X5□18




Size: M30 E2EW-(Q)X10 30




Monitor Output vs. Sensing Distance

PREMIUM Model


Quadruple distance model/ Spatter-resistant Quadruple distance model Shielded



Size: M18 E2EW-(Q)X12□18




Size: M30 E2EW-(Q)X22□30




Triple distance model/ Spatter-resistant Triple distance model Shielded







Size: M18 E2EW-(Q)X10□18







I/O Circuit Diagrams/Timing charts



In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less.

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector



omron 17


PNP output

					Tin	ning chart				
	Operation	Nonsensing area	Unstable Sensing area	Set positi Stable Sensing a	+	-	mity judgment distance ⁷			
Output mode	mode ¹	Sensing object Rated S (%)	ensing dista 100 8	1	20		tySensor			
	NO			1 1 1 1 1 1 1 1 1 1 1 1		ON OFF ON OFF	Comunication indicator (green) : Always OFF Operation indicator (orange)			
						ON OFF	Control output ³			
Standard I/O mode	NC					ON OFF ON OFF ON	Comunication indicator (green) : Always OFF Operation indicator (orange)		utput can be se ommunications N delay, OFF (NOFF delay fu	on of the control et up by the IO-Link . (It is able to selec delay, one-shot, or unction and select a
(SIO mode) ²				1 1 1 1 1 1		OFF	Control output ³		ner time of 1 to ON delay	o 16,383ms (T).) OFF delay
	NO+NC			1 1 1 1 1 1 1		ON OFF ON OFF ON	Comunication indicator (green) : Always OFF Operation indicator (orange) Control output 1 ³		Not present NO ON 1 OFF 0 OFF 0 T+ T+	Sensing Present object Not present NO OFF 0 NC ON 1
				- - - - - -		OFF ON OFF	Control output 2 ³		One shot	ONOFF delay
						Flashing (1sec cycle) ON OFF	Comunication indicator (green) Operation indicator (orange)		NO ON 1 NC OFF 0 NC OFF 0 NC OFF 0	Sensing Present object Not ON 1 OFF 0 OFF 0
	NO			1	1	1	Control output (PD1_bit0) ³			roximity diagnosis
			5		4	1 0 1 0	Instability detection ⁶ (PD1_bit4) Excessive proximity detection (PD1_bit5)	Li 5. Ti	ink communica	etection diagnosis
						Flashing (1sec cycle)	Comunication indicator (green)	6. T	, 0	ne for the instabilit
				1 1 1 1 1		ON OFF	Operation indicator (orange)	by	y the IO-Link c	ommunications.
IO-Link Communication	NC			1 1 1 1 1		1 - 0	Control output (PD1_bit0) ³	(iı	etting can be so nvalid), 10, 50,	elected from 0 100, 300, 500, or
mode (COM mode)			5	1		1 - 0 - 1	Instability detection ⁶ (PD1_bit4) Excessive proximity detection (PD1_bit5)	7. T	000 ms.) he judgment di	
					4	0		fu	xcessive proxir inction can be ink communica	selected by the IO-
						Flashing (1sec cycle) ON	Comunication indicator (green)	() C	The distance ca ombination of t	an be selected as a he material of the
				1		OFF	Operation indicator (orange)	al		IS and the judgmen
	NO+NC			1 1 1 1		0 1	Control output1 (PD1_bit0) ³ Control output2 (PD1_bit1) ³	30	0%. However, i	oximately 10, 20, or it is not allowed to ation of aluminum
			5			- 0	Instability detection ⁶ (PD1_bit4)	a	nd 10%.)	
				1 1 1 1	4	0 1 0	Excessive proximity detection (PD1_bit5)	repre		OMRON sales ding the IO-Link

Please contact your OMRON sales representative regarding assignment of data.

1. For models with IO-Link, the operation mode can be changed by the IO-Link communications.

2. If using a model with IO-Link as a general sensor or using a model without IO-Link, it operates in the standard I/O mode (SIO mode).



Connector Pin Arrangement

M12 Connector M12 Smartclick Connector

Operation mode	Model	Timing chart	Output circuit
NO	E2EW-(Q)X□C1	Nonsensing area Stable sensing area Sensing object Image: Constraint of the sensing distance (%) 100 0 ON OPFF Orange) ON OFF Control output	DC10 to 30V Brown (1) +V Load UUT Black (4) Blue (3) 0V
NC	E2EW-(Q)X□C2	Nonsensing area Stable sensing area Sensing object Image: Constraint of the sensing distance Rated Sensing distance ON (%) 100 OFF (orange) ON OFF Control output	DC10 to 30V Brown (1) +V Load V Black (2) Blue (3) OV
NO+NC	E2EW-(Q)X□C3	Nonsensing area Stable sensing area Sensing object Image: Control output 1 Rated Sensing distance ON (%) 100 OR Operation indicator (orange) ON OFF ON OFF	DC10 to 30 Brown (1) Load Load Black (4) OUT1 white (2) OUT2 Blue (3) C

Connector Pin Arrangement






20 OMRON





Operation mode	Model	Timing chart	Output circuit		
NO	E2EW-(Q)X□C1	Nonsensing area Stable sensing area Sensing object Image: Constraint of the sensing distance Rated Sensing distance Image: Constraint of the sensing distance (%) 100 ON Operation indicator OFF (orange) ON OFF OFF Control output	DC10 to 30V Brown (1) +V Load Ucad Circuit Circuit Black (4) Blue (3) 0V		
NC	E2EW-(Q)X□C2	Nonsensing area Stable sensing area Sensing object Image: Constraint of the sensing distance Rated Sensing distance Image: Constraint of the sensing distance (%) 100 ON Operation indicator OFF (orange) ON OFF OFF Control output	DC10 to 30V Brown (1) +V Load V Black (2) Blue (3) OV		
NO+NC	E2EW-(Q)X□C3	Nonsensing area Stable sensing area Sensing object Image: Constraint of the sensing distance (%) 100 ON Operation indicator (%) 0 ON Operation indicator OFF (orange) ON OFF OFF Control output 1 OFF OFF OFF Control output 2	DC10 to 30V Brown (1) +V Load Load Black (4) OUT1 white (2) OUT2 Blue (3) OV		

Connector Pin Arrangement



Connections for Sensor I/O Connectors

DC 3-Wire

Proximity Sensor				Sensor I/O Connectors		
Types	Output	Operation mode	Model	Model	Connections ¹	
DC 3-Wire (M12 Connector)		NO	E2EW-(Q)X□B1□- M1TJ/M1		EZEW Series X52	
	PNP	NC	E2EW-(Q)X□B2□-M1TJ/M1	XS2F- M12□□□4□□M	E2EW Series XS2 2 Brown (+) O White (Output) O Blue (-) O Black (not connected)	
		NO+NC	E2EW-(Q)X□B3□-M1TJ/M1		E2EW Series X52 U U U U U U U U U U U U U U U U U U U	
		NO	E2EW-(Q)X□C1□-M1TJ/M1	XS2W-D42	EZEW Series X52 U U U U U U U U U	
	NPN	NC	E2EW-(Q)X□C2□-M1TJ/M1		E2EW Series XS2 2 Brown (+) White (Output) Blue (-) Black (not connected)	
		NO+NC	E2EW-(Q)X□C3□-M1TJ/M1		E2EW Series XS2	

If the XS2W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.
 Different from Proximity Sensor wire colors.

Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.automation.omron.com/. Warning Indications

∕∆ WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

\bigcirc	General prohibition Indicates the instructions of unspecified prohibited action.
	Caution, explosion Indicates the possibility of explosion under specific conditions.

🕂 WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Otherwise, explosion may result. Never use the product with an AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- 1. Do not use the product in environments subject to flammable or explosive gases.
- 2. Do not attempt to disassemble, repair, or modify the product.
- 3. Do not use a voltage that exceeds the rated operating voltage range

Applying a voltage that is higher than the operating voltage range may result in explosion or fire.

- 4. Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or fire.
- 5. If the power supply is connected directly without a load, the internal elements may explode or burn.
- 6. Dispose of the product according to applicable regulations (laws).

Precautions for Correct Use

Do not use the product in any atmosphere or environment that exceeds the ratings.

Operating Environment

- 1. Do not install the Sensor in the following locations. (1) Outdoor locations directly subject to sunlight, rain, snow,
 - waterdroplets, or oil. (2) Locations subject to atmospheres with chemical vapors, inparticular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- 3. Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- 4. Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- 5. When turning on the power by influence of temperature environment, an outputmis-pulse sometimes occurs. After the sensor has passed for 300 msec after turning on, please use in the stable state.
- 6. The sensor is adjusted with a high degree of accuracy, so do not use in the environment with sudden temperature change.
- 7. Operation check is performed using an OMRON's IO-Link master. If using an IO-Link master from another company, perform the operation check in advance.
- 8. When connecting non IO-Link compliant models to the IO-Link master, use the SIO mode.
- 9. In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less.
- 10. The Sensor cannot be used embedded in where pressure is constantly applied to the sensing surface, such as hydraulic cylinders and hydraulic valves.


Design

Influence of Surrounding Metal

When mounting the Proximity Sensor, ensure that the minimum distances given in the following table are maintained.

If you use a nut, only use the provided nut. And ensure that the minimum distances between the sensing surface and nut is bigger than the "L" given in the following table.

Other non-ferrous metals affect sensor's performance in the same way as aluminum. Perform the operation check in advance.



(Unit: mm)

Mounting panel material: Iron


Models	Model	L	d	D	m	n
	E2EW-(Q)X7□12	4	30	4	28	36
Quadruple distance model	E2EW-(Q)X12□18	6	54	6	36	54
	E2EW-(Q)X22□30	8	90	8	66	90
	E2EW-(Q)X6□12	4	30	4	24	36
Triple distance model	E2EW-(Q)X10□18	2	54	2	30	54
	E2EW-(Q)X20□30	0	30	0	60	90
	E2EW-(Q)X2□12	0	12	0	8	40
Single distance model	E2EW-(Q)X5□18	0	18	0	20	60
moder	E2EW-(Q)X10□30	0	30	0	40	100

Mounting panel material: Aluminum

Models	Model	L	d	D	m	n
	E2EW-(Q)X7□12	12	70	12	28	70
Quadruple distance model	E2EW-(Q)X12□18	12	80	12	36	80
	E2EW-(Q)X22□30	16	120	16	66	120
	E2EW-(Q)X6□12	12	70	12	24	70
Triple distance model	E2EW-(Q)X10□18	12	80	12	30	80
	E2EW-(Q)X20□30	16	120	16	60	120
	E2EW-(Q)X2□12	12	70	12	8	70
Single distance model	E2EW-(Q)X5□18	12	80	12	20	80
	E2EW-(Q)X10□30	16	120	16	40	120

1. If you use the model E2EW-(Q)X22□30, or E2EW-(Q)X20□30, the panel thickness (t) is 3 mm or less.

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



Embedded material: Iron

Models	Model	I	d	D	m	n
	E2EW-(Q)X7□12	4	30	4	28	36
Quadruple distance model	E2EW-(Q)X12□18	6	54	6	36	54
	E2EW-(Q)X22□30	8	90	8	66	90
	E2EW-(Q)X6□12	0 ²	12 ²	0 ²	24	36
Triple distance model	E2EW-(Q)X10□18	0	18	0	30	54
modor	E2EW-(Q)X20□30	0	30	0	60	90
	E2EW-(Q)X2□12	0	12	0	8	40
Single distance model	E2EW-(Q)X5□18	0	18	0	20	60
moder	E2EW-(Q)X10□30	0	30	0	40	100

(Unit: mm)


*2. If the thickness of the mounting bracket (t) is less than 10 mm, be sure to install the Sensor so that $I \ge 2$, d (dia.) ≥ 30 , and $D \ge 2$.

Embedded material: Aluminum

Models	Model	I	d	D	m	n
	E2EW-(Q)X7□12	12	70	12	28	70
Quadruple distance model	E2EW-(Q)X12□18	12	80	12	36	80
distance moder	E2EW-(Q)X22□30	16	120	16	66	120
	E2EW-(Q)X6□12	12	70	12	24	70
Triple distance model	E2EW-(Q)X10□18	12	80	12	30	80
	E2EW-(Q)X20□30	16	120	16	60	120
	E2EW-(Q)X2□12	12	70	12	8	70
Single distance model	E2EW-(Q)X5□18	12	80	12	20	80
mouor	E2EW-(Q)X10□30	16	120	16	40	120

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sidebyside, ensure that the minimum distances given in the following table are maintained.



(Unit: mm)

Models	Model	lte	m
woders	Woder	Α	В
	E2EW-(Q)X7□12	45	40
Quadruple distance model	E2EW-(Q)X12□18	80	60
	E2EW-(Q)X22□30	135	110
	E2EW-(Q)X6□12	45	40
Triple distance model	E2EW-(Q)X10□18	80	60
mouor	E2EW-(Q)X20□30	135	110
	E2EW-(Q)X2□12	40	35
Single distance model	E2EW-(Q)X5□18	65	60
	E2EW-(Q)X10□30	110	100

Chips from Cutting Aluminum


Normally, chips from cutting aluminum will not cause a detection signal to be output even if it adheres to or accumulates on the detection surface. In the following cases, however, a detection signal may be output.

Remove the cutting chips in these cases.

1. If $d \ge 2/3D$ at the center of the detection surface where d is the cutting chip size and D is the detection surface size

		(Unit: mm)
Model	Dimension	D
E2EW-(Q)X□12		10
E2EW-(Q)X□18		16
E2EW-(Q)X□30		28

2.If the cutting chips are pressed down





Mounting

Tightening Force

Do not tighten the nut with excessive force.

A washer must be used with the nut.

The tightening force must be the same or less than the figures in the following table.



Quadruple distance model, Triple distance model (Unit: N·m)

Size	Torque
M12	20 (15)
M18	70 (35)
M30	180 (60)

* Tighten the nut of the E2EW-Q to a torque in parentheses.

Single distance model

Unit: N·m				
Size	Torque			
M12	30 (15)			
M18	70 (35)			
M30	180 (60)			

* Tighten the nut of the E2EW-Q to a torque in parentheses.

Note: When mounting the Proximity Sensor, only use the provided nut. Do not use set screws. The Sensor may malfunction.


Dimensions

Sensors

PREMIUM Model

del E2EW/E2EW-Q Series

(Quadruple distance/Triple distance/Spatter-resistant Quadruple distance, Spatter-resistant Triple distance model)



Mounting Hole Dimensions

□12(-M1TJ)

□18(-M1TJ)

30(-M1TJ)

E2EW-(Q)X10

E2EW-(Q)X20

M18×P1

M30×P1.5

41.5 30 4 13

41.5 30 5 13

Triple

model

distance


Angle R of the Bending Wire

24

36

29 dia.

42 dia.



Dimensions

(Unit: mm) Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.

Sensors

BASIC Model


M30

F

30.5 dia.

+0.5

E2EW/E2EW-Q Series (Single distance model/Spatter-resistant Single distance model)



M30

R

27



OMRON AUTOMATION AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • automation.omron.com

OMRON CANADA, INC. • HEAD OFFICE Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • automation.omron.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE Ciudad de México • 52.55.5901.4300 • 01.800.386.6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE San Pedro Garza García, N.L. • 81.12.53.7392 • 01.800.386.6766 • mela@omron. com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE Eugenio Garza Sada,León, Gto • 01.800.386.6766 • mela@omron.com

Authorized Distributor:

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE São Paulo, SP, Brasil • 55 11 5171-8920 • automation.omron.com

OMRON ARGENTINA • SALES OFFICE Buenos Aires, Argentina • +54.11.4521.8630 • +54.11.4523.8483 mela@omron.com

OTHER OMRON LATIN AMERICA SALES +54.11.4521.8630 • +54.11.4523.8483 • mela@omron.com

Controllers & I/O

Machine Automation Controllers (MAC)
 Motion Controllers

Programmable Logic Controllers (PLC)
 Temperature Controllers
 Remote I/O

Robotics

Industrial Robots
 Mobile Robots

Operator Interfaces

• Human Machine Interface (HMI)

Motion & Drives

- Machine Automation Controllers (MAC)
 Motion Controllers
 Servo Systems
- Frequency Inverters

Vision, Measurement & Identification

Vision Sensors & Systems • Measurement Sensors • Auto Identification
Systems

Sensing

- Photoelectric Sensors Fiber-Optic Sensors Proximity Sensors
- Rotary Encoders
 Ultrasonic Sensors

Safety

Safety Light Curtains
 Safety Laser Scanners
 Programmable Safety Systems

- Safety Mats and Edges Safety Door Switches Emergency Stop Devices
- Safety Switches & Operator Controls Safety Monitoring/Force-guided Relays

Control Components

- Power Supplies
 Timers
 Counters
 Programmable Relays
- Digital Panel Meters
 Monitoring Products

Switches & Relays

- Limit Switches
 Pushbutton Switches
 Electromechanical Relays
- Solid State Relays

Software

Programming & Configuration
 Runtime

© 2021 Omron. All Rights Reserved.

Printed in U.S.A.