



Push-in Switches & Pilot Lights

Simple wiring with Push-in technology

IDEC CORPORATION





All thoughts focused on the same goal

Since the late 1970s, IDEC has continued to instill and pursue "Save and Safe", as part of our corporate DNA. Along with the rapid advancement in machine intelligence and demands for environmental resistance and high reliability in recent years, we need to face societal issues such as shortage in workforce.

To solve these issues, we have set as our goals "Safe, Simple & Smart=S³ (S cube)", aiming to provide society with products and services that will bring about greater innovation and lasting quality.

Safe

Products anyone can use with safety and assurance, from a company seeking to be number one in safety

Simple

Products appreciated by all our customers for their ease of connection regardless of experience

Smart

Products that make labor-saving and space-saving a reality




We provide easy and user-friendly products with new technology.

First in the industry Six different colors with a single LED


Previously, 5 different color LEDs were required but with the new illuminated LED unit, only a single LED is used. Only the lens needs to be replaced to change the illumination color.

The new LED reduces maintenance time, makes stock control easier, and is environmentally friendly.





Brighter and clearer compared to conventional LEDS



ISO3864-4 Safety color compliant

Safety colors are defined with ISO standards.

The bright and clears colors are suited for emergency situations

^{*}Except for products below

[•]Illuminated selector switches (illumination color: S (Blue), PW (Pure white))

[•]Illuminated pushbuttons (illumination color: S (Blue))

Push-in

Smart Simple

Simple wiring for greater work efficiency

Ferrules and solid wires can be connected simply by push-in insertion, without a screwdriver. (*1) To remove, a flat-blade screwdriver is inserted in a simple two-action process. Since wiring can be performed regardless of operators' skill level,

*1) When connecting stranded wire, insert the wire while holding down the pusher with a flat-blade screwdriver.

wiring time is reduced.




Push the wire straight in as far as it will go.



Connection is completed. Pull lightly to make sure it is firmly in place.



Hold down the pusher with a flat-blade screwdriver.




While holding down the pusher, pull out the wire. Release the flat-blade screwdriver.

Time saving and efficient

Push-in connections are made simple by inserting the wire, reducing wiring time by approximately 55% compared to conventional screw terminals.

[Conditions]

Push-in: Insert wire with ferrule. Screw terminals: With screw loosened, insert wire, then tighten with electric driver.



*2) As of IDEC research (as of January 2020)

Reliable and easy


Finger-safe structure and vibration resistance. What's more, the space-saving design means better workability in a smaller space.

Stays firmly in place

Since the ferrule is held in place by a spring load, the wiring remains taut and vibration resistance is improved.

Finger-safe structure

IP20 Finger-safe protection enables wiring to be performed without direct contact between screwdriver and conductive part.



Smart Simple

Wiring procedure comparison

Work can be performed without using tools and regardless of operators' skill level.

*1) When ferrule is used.

Conventional screw terminal

Remove Pass wire through crimping terminal screw

Tighten screw

Check

Push-in terminal (*1)

Insert wire

Simple one-step operation

Pull lightly to confirm

No additional tightening needed

Because screws are not used on push-in terminals, re-tightening of screws is not required.

Product Upgrade

The superior functions of the conventional HW Series still remain while improving ease of use.

Space-Saving

Contact block depth reduced

Saves space inside panel and enables downsizing of equipment.

Pilot light full voltage type



Panel depth reduced by

50% DOWN



Push-in HW Series

Conventional HW Series

Illuminated pushbuttons 6V, 12V, 24V AC/DC



Panel depth reduced by

30% DOWN



Push-in HW Series

Conventional HW Series

NEW

Illuminated pushbuttons 100/120V AC/DC, 200/220V AC, 230/240V AC



Conventional HW Series

Panel depth reduced by

40% DOWN



 \rightarrow

Push-in HW Series

No transformers required for high voltage types



Smart

High-voltage pilot lights No transformer required

Applicable for a wide range of voltage (100/120V AC/DC, 200/240V AC). Mounts directly on control and power panels without transformers.

Ideal for use in Europe and north America for applications requiring high voltage.



Locking lever

Usability improved by easy mounting and removal. The mounting status of the contact blocks can be confirmed at a glance from the back of the switch.





The specifications are the same as the conventional series, enabling easy installation



Panel design

Push-in design does not change the panel design.



Electrical rating and durability

Same electrical ratings and durability with push-in terminal contact blocks.

4-contact configuration available with double contact blocks

Double contact blocks available for all models including emergency stop switches, selector switches, key selector switches.

Double contact blocks

Single contact blocks









NEW

High voltage LED illuminated unit for illuminated pushbuttons

100/120V AC/DC, 200/220V AC, 230/240V AC types available. No transformers required and same depth behind the panel for for all illuminated voltages. High voltage models do not require transformers enabling downsizing of equipment and panels. 1-contact types also available.

Conventional screw terminal Push-in models do not

Push-in

require transformers compared with conventional screw models enabling downsizing of equipment

100/120V AC/DC, 200/220V AC, 230/240V AC types

Angled connections

Angled connections make wiring easy even when switches are mounted on a panel.

Also, 24-degree inclination faced to the panel improves the fit of the wires, and contributes to downsizing of the panel and equipment.



Added Value

Our aim is to create products that enable customers to experience the utmost usability.

Test point

A test point is available to check connectivity of the wiring. Check the connectivity easily using a tester.



Sub-Assembled Units

Sub-assembled units can be ordered for flexible use, such as sudden changes in design.



Ø22 HW Series Push-in Switches & Pilot Lights

- Push-in terminal connection reduces wiring time.
- · Safety enhanced with IP20 finger-safe protection.









· See website for details on approvals and standards.

Note) Approvals for pushbuttons, selector switches, pilot lights only.

For illuminated/non-illuminated buzzer (page 45) and emergency stop switches (page 46), see each page.

Specifications and Ratings

Contact Ratings

Pushbuttons Illuminated Pushbuttons Dual Pushbuttons Selector Switches Key Selector Switches Illuminated Selector Switches Selector Pushbuttons Monolever Switches Emergency Stop Switches	Rated insulation voltage Rated continuous current	600V 10A
	Contact ratings by utilization category IEC60947-5-1	AC-15 (A600) DC-13

[•] See website for approved contact ratings.


Rated Operating Voltage and Current by Utilization Category

HW-P10 (NO contact), HW-P01 (NC contact), HW-PW20 (2NO contact), HW-PW11 (1NO-1NC contact), HW-PW02 (2NC contact)

Operating Voltage		24V	48V	50V	110V	220V	440V	
	AC	AC-12 Control of resistive loads and solid state loads	10A	-	10A	10A	6A	2A
Operating	50/60 Hz	AC-15 Control of electromagnetic loads (> 72 VA)	10A	-	7A	5A	3A	1A
Current	DC	DC-12 Control of resistive loads and solid state loads	10A	5A	_	2.2A	1.1A	-
	DC	DC-13 Control of electromagnets	5A	2A	_	1.1A	0.6A	_

- The operating current represents making and breaking currents (IEC 60947-5-1).
- · Contact materials: Silver contacts
- Minimum applicable load: 3V AC/DC, 5 mA (applicable range may vary with operating conditions)

Push-in Contact Block (HW-P)



	Single Cor	ntact Block	Block Double Contact Block		
Contact	1NO	1NC	2N0	2NC	1NO-1NC
Part No.	HW-P10	HW-P01	HW-PW20	HW-PW02	HW-PW11
Shape		The same			
Housing	Blue	Purple red	Blue	Purple red	Blue/Purple red
Push Rod	Green	Red	Green	Red	Light Blue
Contact No.	3-4	1-2	1st deck: 13-14 2nd deck: 23-24	1st deck: 11-12 2nd deck: 21-22	1st deck: 13-14 2nd deck: 21-22
Weight	8g		16g		

LED Illuminated Part Specifications

Illuminated Pushbuttons, Illuminated Selector Switches, Dual Pushbuttons (with pilot light)

Rated Voltage	Operating Voltage		LED Lamp		
nateu voitage			Ramp Base	Part No.	
6V AC/DC	6V AC/DC			LSRD-6	
12V AC/DC	12V AC/DC			LSRD-1	
24V AC/DC	24V AC/DC	±10%	BA9S/13	LSRD-2	
100/120V AC/DC	100/120V AC/DC		DA95/13	LSRD-H2	
200/220V AC	200/220V AC			LSRD-M2	
230/240V AC	230/240V AC	207~250V		LSRD-M4	

Pilot Light

Rated Voltage		Operating	Operating Voltage		LED Lamp	
		Operating Voltage		Ramp Base	Part No.	
6V AC/DC		6V AC/DC			LSRD-6	
12V AC/DC		12V AC/DC	C	BA9S/13	LSRD-1	
24V AC/DC		24V AC/DC	±10%		LSRD-2	
100/120V AC	50/COLL-	100/120V AC			LSRD-6	
200/240V AC	50/60Hz	200/240V AC			ี	

LED Lamp Ratings

Part No.		LSRD-6	LSRD-1	LSRD-2	LSRD-H2	LSRD-M2	LSRD-M4
Ramp Base		BA9S/13					
Rated Voltage		6V AC/DC	12V AC/DC	24V AC/DC	100/120V AC/DC	200/220V AC	230/240V AC
Voltage Range		6V AC/DC ±10%	12V AC/DC ±10%	24V AC/DC ±10%	100/120V AC/DC ±10%	200/220V AC ±10%	230/240V AC ±10%
Current Draw	DC	10mA	7mA	7mA	2mA	2mA	2mA
Current Draw	AC	14mA	8mA	8mA	2mA	2mA	2mA
Life (reference	value)	Approx. 50,000 hours	(The luminance is redu	iced to 50% the initial ir	ntensity when used on o	omplete DC at 25°C.)	
Life (reference value) Approx. 50,000 hours (The luminance is reduced to 50% the initial intensity when used on complete DC at 25°C.) X1 — Limited current circuit Noise protection circuit Rectifier circuit Dimmer protection circuit							

Direct Opening of Key Selector Switch

	,	
Applicable Type	2-position	3-position
Minimum Operator Angle for Direct Opening Action	60° (90° Maintained)	45°
Minimum Operator Torque for Direct Opening Action	0.4 N·m	
Maximum Operator Angle	60° (90° Maintained)	45°

Degree of Protection

IEC60529

Unit	IEC 60529
All models except Illuminated selector switches, dual pushbuttons, pilot lights	IP65 (*1)
Illuminated selectors, pilot lights	IP65
Dual pushbuttons	IP40 (*2)

^{*1)} When using a nameplate with the HW series, IP65 protection degree is achieved only when nameplates shown on page 50 are used. (IP40 when other ø22 namplates such as NWA are used)
*2) IP65 when used with button covers (HW9Z-D7D).

UL50

Unit	UL50
All models except illuminated selector switches	Type 4X (*3)(*4)

^{*3)} When using a nameplate with the HW series, IP65 protection degree is achieved only when nameplates shown on page 50 are used.

^{*4)} For dual pushbuttons, Type 4X is acheived when used with button covers (HW9Z-D7D).

Specifications

Switches (except for emergency stop switch)

OWITOTIOS (OXOOPT TOT O	mergency stop switch)
Operating Temperature	-25 to +60°C (no freezing) Illuminated unit: -25 to +50°C
Operating Humidity	45 to 85% RH (no condensation)
Storage Temperature	-40 to +80°C (no freezing)
Contact Resistance	50 mΩ maximum (initial value)
Insulation Resistance	100 MΩ minimum (500V DC megger)
Overvoltage Category	II
Impulse Withstand Voltage	4.0kV Illuminated unit: 2.5kV
Pollution Degree	3 (IEC60947-5-1)
Dielectric Strength	Between live and dead parts: 2500V AC, 1 minute
Vibration Resistance	Damage limits: 30 Hz, amplitude 1.5 mm Operating extremes: 5 to 55Hz, amplitude 0.5 mm
Shock Resistance	Damage limits: 1,000 m/s ² Operating extremes: 100 m/s ²
	Terminal: Finger-safe (IP20) structure
Degree of Protection Recommended Tightening	Panel front: IP65 (IEC 60529), UL Type 4X
Torque for Locking Ring	2.0N·m
Terminal Style	Push-in terminal
	Pushbuttons, Illuminated Pushbuttons Momentary
	1,000,000 (*5)
	Maintained
	100,000 (*6)
Mechanical Life (minimum operations)	Dual pushbuttons
	Selector switches 500.000 (*5)
	100,000 (*6)
	Key selector switches (Disc tumbler)500,000 (*5) 100,000 (*6)
	Key selector switches (Pin tumbler) 100,000 (*5) 100,000 (*6)
	Illuminated selector switches 500,000 (*5) 100,000 (*6)
	Selector pushbuttons 250,000 (*5)
	100,000 (*6) Monolever switches250,000 (*5)
	100,000 (*6)
	Pushbuttons, Illuminated Pushbuttons
	Momentary 500,000 (*1)(*5)
	50,000 (*1)(*6) Maintained500,000 (*3)(*5)
	500,000 (*3)(*5)
	Dual pushbuttons500,000 (*1)(*5)
	50,000 (*1)(*6)
	Selector switches500,000 (*2)(*5) 50,000 (*2)(*6)
Electrical Life (*5)	Key selector switches (Disc tumbler)500,000 (*2)(*5) ·50,000 (*2)(*6)
	Key selector switches (Pin tumbler)100,000 (*2)(*5)
	50,000 (*2)(*6) Illuminated selector switches500,000 (*2)(*5)
	50,000 (*2)(*6) Selector pushbuttons250,000 (*2)(*5)
	50,000 (*2)(*6) Monolever switches250,000 (*3)(*5)
	50,000 (*3)(*6)
	38g (HW1B-M1P11), 54g (HW1B-M1P22)
	38g (HW1S-2TP11), 54g (HW1S-2TP22) 76g (HW1K-2AP11), 92g (HW1K-2AP22N2)
Weight (approx.)	66g (HW1K-2PCP11), 45g (HW1L-M1P11Q4)
	44g (HW1F-2P11Q4), 43g (HW1R-2AP11)
	55g (HW1M-1010P-20), 45g (HW7D-B11P1001)

- *1) Switching frequency 1,800 operations/h, duty ratio 40%
- *2) Switching frequency 1,200 operations/h, duty ratio 40%
- *3) Switching frequency 900 operations/h, duty ratio 40%
- *4) Load condition 220V AC, 3A (AC-15)
- *5) Single contact block
- *6) Double contact block


Pilot lights

Operating Temperature	-25 to +50°C (no freezing)		
Operating Humidity	45 to 85% RH (no condensation)		
Storage Temperature	-40 to +80°C (no freezing)		
Insulation Resistance	100 MΩ minimum (500V DC megger)		
Overvoltage Category	II		
Impulse Withstand Voltage	2.5kV		
Pollution Degree	3		
Dielectric Strength	Between live and dead parts: 2000V AC, 1 minute		
Vibration Resistance	Damage limits: 30 Hz, amplitude 1.5 mm Operating extremes: 5 to 55Hz, amplitude 0.5 mm		
Shock Resistance	Damage limits: 1,000 m/s ²		
SHOCK NESISTANCE	Operating extremes: 100 m/s ²		
Degree of Protection	Terminal: Finger-safe (IP20) structure Panel front: IP65 (IEC 60529), UL Type 4X		
Recommended Tightening Torque for Locking Ring	2.0N·m		
Terminal Style	Push-in terminal		
Weight (approx.)	26g (HW1P-2JPQ4) 27g (HW1P-2JPRH2) 28g (HW1P-2JPCM2)		

Mounting Hole Layout

(Dimensions in mm)

Panel Cut (IEC60947-5-1)



- When high temperature is expected, take necessary measures such as securing sufficient mounting centers or using a cooling fan.
- The 3.2 mm recess is for preventing rotation and is not necessary when the nameplate or anti-rotation ring is not used.

Minimum Mounting Centers

(Dimensions in mm)

Unit	Vertical (*7)	Horizontal (*8)
ø40mm mushroom buttons	50	40
Selector pushbuttons	50	50
Monolever switches	72	72
Pilot lights	50	30
Dual pushbuttons	55	30
Illuminated selector switches	50	50

- For emergency stop switch mounting centers, see page 46.
- Determine the mounting cetners in consideration of the operation, wiring, and testing terminals.

Ordering Information

- Specify the Ordering No. when ordering.
 When ordering, specify button color, lens color, key removal specification, or key number codes.
- Some combinations cannot be ordered. For details, contact IDEC.
- Nameplates and accessories for mono-lever switch are ordered separately. See page 50 to 55.

Illuminated / non-illuminated buzzer specifications: see page 45

Emergency stop switch specifications: see page 46

Pushbuttons

Assembled



Package Quantity: 1

Name / Shape	Operation	Contact Configuration	Part No. (Ordering No.)	© Color Code
Flush HW1B-M1		1NO	HW1B-M1P10⑤	
HW1B-A1		1NC	HW1B-M1P015	
	Momentary	1NO-1NC	HW1B-M1P115	
		2N0	HW1B-M1P205	
		2NC	HW1B-M1P025	B (black) G (green)
	Maintained	1NO	HW1B-A1P10®	R (red) Y (yellow)
Extended HW1B-M2		1NO	HW1B-M2P105	S (blue) W (white)
	Momentary	1NC	HW1B-M2P015	
		1NO-1NC	HW1B-M2P115	
		2N0	HW1B-M2P205	
		2NC	HW1B-M2P02 ^⑤	

• For other specifications, select from sub-assembled units (page 13 to 14).


Package Quantity: 1

Name / Shape	Operation	Contact	Part No.	5
тамина у втогра		Configuration	(Ordering No.)	Color Code
ø29mm Mushroom HW1B-M3		1NO	HW1B-M3P10⑤	
	Momentary	TNO	IIW IB-M3I IO⊚	
	Momentary	1NC	HW1B-M3P01®	B (black) G (green) R (red)
ø40mm Mushroom HW1B-M4	Momentony	1NO	HW1B-M4P10⑤	Y (yellow) S (blue) W (white)
	Momentary	1NC	HW1B-M4P01®	


- Specify a button color code in place of ⑤ in the Part No.
- Pushbuttons with 1 contact block contain 2 dummy blocks. Pushbuttons with 2 contact blocks contain 1 dummy block.
- When requiring flush type maintained switches other than 1NO contact configuration, select from sub-assembled product.

Pushbuttons Part No. Example

Assembled and sub-assembled unit



 \bullet For available assembled products, see above table.



Pushbuttons

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 12 for available assembled products.



				(5)
Name / Shape	Operation	Contact Configuration	<reference> Assembled Part No.</reference>	Button
	-	Conniguration	Assembled Part No.	Color Code
Flush		1NO	HW1B-M1P10®	
	_	1NC	HW1B-M1P015	
	l om	1NO-1NC	HW1B-M1P115	
T. B.	/lomentar	2N0	HW1B-M1P20®	D (blook)
	Ž	2NC	HW1B-M1P025	B (black) G (green)
		2NO-2NC	HW1B-M1P225	R (red)
		1NO	HW1B-A1P10®	Y (yellow)
	_	1NC	HW1B-A1P015	S (blue) W (white)
	Maintaineo	1NO-1NC	HW1B-A1P115	w (wille)
	laine	2N0	HW1B-A1P20®	
	8	2NC	HW1B-A1P025	
		2NO-2NC	HW1B-A1P225	
Flush		1N0	HW1B-M2P105	
	=	1NC	HW1B-M2P01®	
	Momentary	1NO-1NC	HW1B-M2P11®	
		2N0	HW1B-M2P20®	B (black) G (green)
N. C.		2NC	HW1B-M2P02®	
		2NO-2NC	HW1B-M2P225	R (red)
	Maintainec	1NO	HW1B-A2P10®	Y (yellow)
		1NC	HW1B-A2P01®	S (blue) W (white)
		1NO-1NC	HW1B-A2P115	w (wille)
		2N0	HW1B-A2P20®	
	8	2NC	HW1B-A2P025	
		2NO-2NC	HW1B-A2P225	
ø29mm		1NO	HW1B-M3P10®	
Mushroom	S	1NC	HW1B-M3P01®	
	om e	1NO-1NC	HW1B-M3P11®	
	Vlomentar	2N0	HW1B-M3P20®	B (black)
	2	2NC	HW1B-M3P02®	G (green)
		2NO-2NC	HW1B-M3P225	R (red)
		1NO	HW1B-A3P10®	Y (yellow)
	S	1NC	HW1B-A3P01®	S (blue) W (white)
	aint	1NO-1NC	HW1B-A3P11®	w (wille)
	Maintained	2N0	HW1B-A3P20®	
	ğ	2NC	HW1B-A3P025	
		2NO-2NC	HW1B-A3P22®	

Sub-Assemble		ı			ackage Quantity: 1
Opera	ator Unit			Contact Unit	
Name / Shape	Part No. (Ordering No.)		Shape	Contact Configuration	Part No. (Ordering No.)
Flush				1NO	HW-CNP10
	HW1B-M1⑤-PS		Ø	1NC	HW-CNP01
				1NO-1NC	HW-CNP11
				2N0	HW-CNP20
	HW1B-A1®-PS		O	2NC	HW-CNP02
				2NO-2NC	HW-CNP22
Extended				1NO	HW-CNP10
	HW1B-M2®-PS HW1B-A2®-PS		O	1NC	HW-CNP01
			1NO-1NC	HW-CNP11	
			2N0	HW-CNP20	
			2NC	HW-CNP02	
			2NO-2NC	HW-CNP22	
ø29mm Mushroom				1NO	HW-CNP10
	HW1B-M3®-PS HW1B-A3®-PS		Ó	1NC	HW-CNP01
				1NO-1NC	HW-CNP11
				2N0	HW-CNP20
			0	2NC	HW-CNP02
				2NO-2NC	HW-CNP22

 $[\]bullet$ Specify a button color code in place of 5 in the Part No. B (black), G (green), R (red), Y (yellow), S (blue), W (white)

Pushbuttons

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 12 for available assembled products.

Name / Shape	Operation	Contact Configuration	<reference> Assembled Part No.</reference>	⑤ Button Color Code
40mm		1NO	HW1B-M4P10®	
/lushroom	_	1NC	HW1B-M4P01®	
	Momentary	1NO-1NC	HW1B-M4P11®	
	nent	2NO	HW1B-M4P20®	
	ary	2NC	HW1B-M4P02®	B (black)
		2NO-2NC	HW1B-M4P22®	G (green)
		1NO	HW1B-A4P105	R (red) Y (yellow)
		1NC	HW1B-A4P01®	S (blue)
	Maintained	1NO-1NC	HW1B-A4P115	W (white)
	ntai			
	ned	2N0 2NC	HW1B-A4P20® HW1B-A4P02®	-
0mm		2NO-2NC	HW1B-A4P225	
ıshroom		1NO	HW1B-M5P10®	
		1NC	HW1B-M5P01®	
	Mom	1NO-1NC	HW1B-M5P11®	B (black)
	Momentary	2N0	HW1B-M5P20®	G (green) R (red)
		2NC	HW1B-M5P02®	
		2NO-2NC	HW1B-M5P22⑤	
quare Flush		1NO	HW2B-M1P105	
		1NC	HW2B-M1P015	
	om	1NO-1NC	HW2B-M1P115	
- 100	Momentary	2N0	HW2B-M1P20®	İ
	ary	2NC	HW2B-M1P02®	B (black)
		2NO-2NC	HW2B-M1P22®	G (green) R (red)
		1NO	HW2B-A1P10®	Y (yellow)
	_	1NC	HW2B-A1P015	S (blue)
	Maintained	1NO-1NC	HW2B-A1P115	W (white
	Itali	2N0	HW2B-A1P20®	-
	Ted	2NC	HW2B-A1P02®	-
		2NO-2NC		-
ıare	 		HW2B-A1P225	
ended		1NO 1NC	HW2B-M2P10®	
	Mor		HW2B-M2P01®	-
	Momentary	1NO-1NC	HW2B-M2P11®	
	tary	2N0	HW2B-M2P20®	B (black)
	`	2NC	HW2B-M2P02®	G (green)
N T		2NO-2NC	HW2B-M2P22®	R (red) Y (vellow)
		1NO	HW2B-A2P10⑤	S (blue)
-	M ₂	1NC	HW2B-A2P01⑤	W (white)
	Maintained	1NO-1NC	HW2B-A2P11⑤	` ′
	ine.	2N0	HW2B-A2P20⑤	
	3	2NC	HW2B-A2P02®	
		2NO-2NC	HW2B-A2P225	

·	ator Unit Part No.
Name / Shape	(Ordering No.)
ø40mm Mushroom	
	HW1B-M4®-PS
	HW1B-A4®-PS
a60mm Mushroom	HW1B-M5⑤-PS (*1)
Square Flush	HW2B-M1®-PS
	HW2B-A1®-PS
Square Extended	HW2B-M2 [®] -PS
	HW2B-A2®-PS

		Package Quantity:
01	Contact Unit	Part No.
Shape	Configuration	(Ordering No.)
	1NO	HW-CNP10
Ø	1NC	HW-CNP01
	1NO-1NC	HW-CNP11
	2N0	HW-CNP20
O	2NC	HW-CNP02
	2NO-2NC	HW-CNP22
	1NO	HW-CNP10
O	1NC	HW-CNP01
	1NO-1NC	HW-CNP11
	2N0	HW-CNP20
O	2NC	HW-CNP02
	2NO-2NC	HW-CNP22
	1NO	HW-CNP10
O	1NC	HW-CNP01
	1NO-1NC	HW-CNP11
	2N0	HW-CNP20
O	2NC	HW-CNP02
	2NO-2NC	HW-CNP22
	1NO	HW-CNP10
O	1NC	HW-CNP01
	1NO-1NC	HW-CNP11
	2N0	HW-CNP20
O	2NC	HW-CNP02
	2NO-2NC	HW-CNP22

[•] Specify a button color code in place of ⑤ in the Part No. B (black), G (green), R (red), Y (yellow), S (blue), W (white)


^{*1)} Only B (black), G (green), R (red) available for ø60mm mushroom.

Pushbuttons Dimensions


All dimensions in mm.

Flush

1 to 2 contacts HW1B-□1P




3 to 4 contacts HW1B-□1P




Extended

1 to 2 contacts HW1B-□2P




3 to 4 contacts HW1B-□2P




ø29mm Mushroom

1 to 2 contacts HW1B-□3P




3 to 4 contacts HW1B-□3P




ø40mm Mushroom

1 to 2 contacts HW1B-□4P



3 to 4 contacts HW1B-□4P




Pushbuttons Dimensions


All dimensions in mm

ø60mm Mushroom

1 to 2 contacts HW1B-M5P




3 to 4 contacts HW1B-M5P



Square Flush


1 to 2 contacts

HW2B-□1P



3 to 4 contacts


HW2B-□1P




Square Extended

1 to 2 contacts


HW2B-□2P





3 to 4 contacts

HW2B-□2P



Illuminated Pushbuttons

Assembled




	_				Package Quantity: 1
Name / Shape	Operation	Rated Voltage	Contact Configuration	Part No. (Ordering No.)	© Illumination Color Code
Round Flush (marking) HW1L-M1		12V AC/DC	1NO	HW1L-M1P10Q36	
HW1L-A1			1NO	HW1L-M1P10Q4®	
	<u> </u>	24V AC/DC	1NC	HW1L-M1P01Q46	
	Momentary	24V AG/DG	1NO-1NC	HW1L-M1P11Q4®	
	ary		2N0	HW1L-M1P20Q4®	R (red) G (green)
		100/120V AC/DC	1NO	HW1L-M1P10QH2®	Y (yellow) A (amber)
		200/220V AC	1NO	HW1L-M1P10QM®	S (blue) PW (pure white)
			1NO	HW1L-A1P10Q4®	(F. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1. 1.
	Maintained	24V AC/DC	1NC	HW1L-A1P01Q46	
	ained	24V AG/DG	1NO-1NC	HW1L-A1P11Q4®	
			2N0	HW1L-A1P20Q4®	
Round Extended (marking) HW1L-M2			1NO	HW1L-M2P10Q4®	R (red)
	Momentary	24V AC/DC	1NO-1NC	HW1L-M2P11Q4®	G (green) Y (yellow) A (amber) S (blue)
			2NO	HW1L-M2P20Q4®	PW (pure white)
Round Extended with Full Shroud (marking) HW1L-MF2			1NO	HW1L-MF2P10Q4®	R (red)
	Momentary	24V AC/DC	1NO-1NC	HW1L-MF2P11Q4®	G (green) Y (yellow) A (amber) S (blue)
			2NO	HW1L-MF2P20Q4®	PW (pure white)
Square Flush (marking) HW2L-M1			1NO	HW2L-M1P10Q4®	
	Mom	041/40/DC	1NC	HW2L-M1P01Q4®	R (red) G (green) Y (yellow)
	Momentary	24V AC/DC	1NO-1NC	HW2L-M1P11Q4®	A (amber) S (blue) PW (pure white)
			2N0	HW2L-M1P20Q4®	,

 $[\]bullet$ Specify an illumination color code in place of $\ensuremath{\textcircled{6}}$ in the Part No.

[•] For other specifications, select from sub-assembled units (page 18 to 19).

Illuminated Pushbuttons

 $\textbf{Sub-Assembled} \ \big| \ \textbf{When ordering, specify the sub-assembled ordering no. See page 17 for available assembled products.}$



Name / Shape	Operation	Contact Configuration	<reference> Assembled Part No.</reference>	⑥ Illumination Color Code
Round Flush	Round Flush		HW1L-M1P1056	
(marking)	-	1NC	HW1L-M1P0156	
	l om	1NO-1NC	HW1L-M1P1156	
	Momentary	2N0	HW1L-M1P2056	R (red)
To be	2	2NC	HW1L-M1P0256	G (green)
		2NO-2NC	HW1L-M1P2256	Y (yellow)
-		1NO	HW1L-A1P1056	A (amber) S (blue)
	-	1NC	HW1L-A1P0156	PW (pure
	lain	1NO-1NC	HW1L-A1P1156	white)
	Maintainec	2N0	HW1L-A1P2056	
	<u>e</u>	2NC	HW1L-A1P0256	
		2NO-2NC	HW1L-A1P2256	
Round		1NO	HW1L-M2P1056	
Extended	~	1NC	HW1L-M2P0156	
(marking)	Momentar	1NO-1NC	HW1L-M2P1156	
	enta	2N0	HW1L-M2P2056	R (red)
	Ŋ	2NC	HW1L-M2P0256	G (green)
		2NO-2NC	HW1L-M2P2256	Y (yellow)
		1NO	HW1L-A2P1056	A (amber) S (blue)
	-	1NC	HW1L-A2P0156	PW (pure
	∕laintainec	1NO-1NC	HW1L-A2P1156	white)
	l tain	2N0	HW1L-A2P2056	
	<u>e</u>	2NC	HW1L-A2P0256	
		2NO-2NC	HW1L-A2P2256	
Round		1N0	HW1L-MF2P1056	
Extended	~	1NC	HW1L-MF2P0156	
with Full	Momentary	1NO-1NC	HW1L-MF2P1156	
Shroud (marking)	enta	2N0	HW1L-MF2P2056	R (red)
(marking)	Į Į	2NC	HW1L-MF2P0256	G (green)
		2NO-2NC	HW1L-MF2P2256	Y (yellow)
		1N0	HW1L-AF2P1056	A (amber) S (blue)
	=	1NC	HW1L-AF2P0156	PW (pure
	Maintainec	1NO-1NC	HW1L-AF2P1156	white)
	l tain	2N0	HW1L-AF2P2056	
	8	2NC	HW1L-AF2P0256	
		2NO-2NC	HW1L-AF2P2256	

 Specify a rated voltage code in place of 	⑤ in t	he Part No.
--	--------	-------------

apara, a randa randga adaa aa pada a a a aa aa aa aa aa							
Code	Rated voltage	Code	Rated voltage				
Q2	6V AC/DC	QH2	100/120V AC/DC				
Q3	12V AC/DC	QM	200/220V AC				
Q4	24V AC/DC	QM4	230/240V AC				

[•] Specify an illumination color code in place of ⑥ in the Part No. R (red), G (green), Y (yellow), A (amber), S (blue), PW (pure white)

Sub-Assembled Ordering No

Operator unit			
Name / Shape	Part No. (Ordering No.)		
Round Flush (marking)	HW1L-M1®-PS		
	HW1L-A1®-PS		
Round Extended (marking)	HW1L-M2®-PS		
	HW1L-A2®-PS		
Round Extended with Full Shroud (marking)	HW1L-MF2@-PS		
	HW1L-AF2@-PS		

Package Quantity:		
Shape	Contact Office Configuration	Part No. (Ordering No.)
	1NO	HW-CNP10Q0
Ó	1NC	HW-CNP01Q0
	1NO-1NC	HW-CNP11Q0
	2N0	HW-CNP20Q0
0	2NC	HW-CNP02Q0
	2NO-2NC	HW-CNP22Q0
	1NO	HW-CNP10Q0
O	1NC	HW-CNP01Q0
	1NO-1NC	HW-CNP11Q0
O	2N0	HW-CNP20Q0
	2NC	HW-CNP02Q0
	2NO-2NC	HW-CNP22Q0
	1NO	HW-CNP10Q0
O	1NC	HW-CNP01Q0
	1NO-1NC	HW-CNP11Q0
	2N0	HW-CNP20Q0
	2NC	HW-CNP02Q0
	2NO-2NC	HW-CNP22Q0

Note) LED lamp is not supplied. When ordering contact units (illuminated) selected LED from below table.

LED lamp (package o	quantity:1)	
Rated Voltage	Part No. (Ordering No.)	
6V AC/DC	LSRD-6	
12V AC/DC	LSRD-1	
24V AC/DC	LSRD-2	
100/120V AC/DC	LSRD-H2	
200/220V AC	LSRD-M2	
230/240V AC	LSRD-M4	

Illuminated Pushbuttons

Name / Shape Operation Contact Configuration Assembled Part No. Color Code					
Square Flush (marking)	Name /	Oneration			_
Money	Shape	Орстаноп	Configuration	Assembled Part No.	
1N0-1NC HW2L-M1P11(5)(6) 2N0 HW2L-M1P20(5)(6) 4 (green) 4 (yellow) A (amber) 5 (blue) PW (pure white) 1N0 HW2L-A1P10(5)(6) 2N0 HW2L-A1P20(5)(6) 2N0 HW2L-A1P20(5)(6) 2N0 HW2L-A1P20(5)(6) 2N0 HW2L-A1P20(5)(6) 2N0-2NC HW2L-A1P20(5)(6) 2N0-2NC HW2L-A1P20(5)(6) 2N0-2NC HW1L-M3P10(5)(6) 2N0 HW1L-M3P20(5)(6) 2N0-2NC HW1L-M3P20(5)(6) 2N0-2NC HW1L-M3P20(5)(6) 2N0-2NC HW1L-A3P10(5)(6) 2N0 HW1L-A3P10(5)(6) 2N0 HW1L-A3P10(5)(6) 2N0 HW1L-A3P20(5)(6) 2N0 HW1L-A3P20(5)(6) 2N0 HW1L-A3P20(5)(6) 2N0 HW1L-A3P20(5)(6) 2N0 HW1L-M4P20(5)(6) 2N0 HW1L-M4P20(5)(6) 2N0 HW1L-M4P20(5)(6) 2N0-2NC HW1L-A4P10(5)(6) 3N0 HW1L-A4P10(5)(6)			1NO	HW2L-M1P1056	
No	(marking)	3	1NC	HW2L-M1P0156	
No		ome	1NO-1NC	HW2L-M1P1156	
No		enta	2N0	HW2L-M1P2056	R (red)
No	-	₹ 7	2NC	HW2L-M1P0256	
NO	0		2NO-2NC	HW2L-M1P2256	, ,
No			1N0	HW2L-A1P1056	
Maintained Mai		=	1NC	HW2L-A1P0156	
Maintained Mai		lain	1NO-1NC	HW2L-A1P1156	white)
Maintained Mai		aine	2N0	HW2L-A1P2056	
Maintained Mai		8	2NC	HW2L-A1P0256	
TNC			2NO-2NC	HW2L-A1P2256	
1N0-1NC	ø29 Mushroom		1N0	HW1L-M3P1056	
2NC	(marking)	=	1NC	HW1L-M3P0156	
2NC		Nomentary	1NO-1NC	HW1L-M3P1156	G (green)
2NC			2N0	HW1L-M3P2056	
A (amber) S (blue) PW (pure white)	FEFT		2NC	HW1L-M3P0256	
NO			2NO-2NC	HW1L-M3P2256	
No			1NO	HW1L-A3P1056	
2NC		~	1NC	HW1L-A3P0156	
2NC		laint	1NO-1NC	HW1L-A3P1156	white)
2NC		tain	2N0	HW1L-A3P2056	
### 100 ##### 100 #### 100 #### 100 ###### 100 ##### 100 ##### 100 ##### 100 ########		ed.	2NC	HW1L-A3P0256	
Mushroom (marking) 1NC HW1L-M4P01\$6 1N0-1NC HW1L-M4P20\$6 2NO HW1L-M4P20\$6 2NC HW1L-M4P22\$6 2N0-2NC HW1L-M4P22\$6 1NO HW1L-A4P10\$6 1NC HW1L-A4P01\$6 1NC HW1L-A4P11\$6 2NO HW1L-A4P11\$6 2NO HW1L-A4P11\$6 2NO HW1L-A4P20\$6 2NC HW1L-A4P20\$6			2NO-2NC	HW1L-A3P2256	
(marking) 1N0-1NC	ø40 Jumbo		1N0	HW1L-M4P1056	
2NC HW1L-M4P02(5)(6) 2N0-2NC HW1L-M4P22(5)(6) 1N0 HW1L-A4P10(5)(6) 1NC HW1L-A4P01(5)(6) 1N0-1NC HW1L-A4P11(5)(6) 2N0 HW1L-A4P20(5)(6) 2NC HW1L-A4P02(5)(6)		~	1NC	HW1L-M4P0156	
2NC HW1L-M4P02(5)(6) 2N0-2NC HW1L-M4P22(5)(6) 1N0 HW1L-A4P10(5)(6) 1NC HW1L-A4P01(5)(6) 1N0-1NC HW1L-A4P11(5)(6) 2N0 HW1L-A4P20(5)(6) 2NC HW1L-A4P02(5)(6)	(marking)	/lom	1NO-1NC	HW1L-M4P1156	
2NC HW1L-M4P02(5)(6) 2N0-2NC HW1L-M4P22(5)(6) 1N0 HW1L-A4P10(5)(6) 1NC HW1L-A4P01(5)(6) 1N0-1NC HW1L-A4P11(5)(6) 2N0 HW1L-A4P20(5)(6) 2NC HW1L-A4P02(5)(6)		enta	2N0	HW1L-M4P2056	R (red)
1NO HW1L-A4P10\$6 S (blue) PW (pure white)		ary	2NC	HW1L-M4P0256	` '
1NO HW1L-A4P1056 S (blue) 1NC HW1L-A4P0156 PW (pure white) 2NO HW1L-A4P2056 2NC HW1L-A4P2056			2NO-2NC	HW1L-M4P2256	, ,
1NC HW1L-A4P01\$6 PW (pure white)			1NO	HW1L-A4P1056	
1NO-1NC HW1L-A4P11(\$)6 White) 2NO HW1L-A4P20(\$)6 2NC HW1L-A4P02(\$)6		>	1NC	HW1L-A4P0156	PW (pure
2NC HW1L-A4P02(5)(6)		/ain	1NO-1NC	HW1L-A4P1156	
2NC HW1L-A4P02(5)(6)		tain	2N0		
2NO-2NC HW1L-A4P2256		led	2NC	HW1L-A4P0256	
			2NO-2NC	HW1L-A4P2256	

 \bullet Specify a rated voltage code in place of $\ensuremath{\mathfrak{G}}$ in the Part No.

Code	Rated voltage	Code	Rated voltage
Q2	6V AC/DC	QH2	100/120V AC/DC
Q3	12V AC/DC	QM	200/220V AC
Q4	24V AC/DC	QM4	230/240V AC

 \bullet Specify an illumination color code in place of \circledR in the Part No. R (red), G (green), Y (yellow), A (amber), S (blue), PW (pure white)

Sub-Assembled Ordering No.

Оре	rator unit
Name / Shape	Part No. (Ordering No.)
Square Flush (marking)	HW2L-M1®-PS
	HW2L-A1®-PS
ø29 Mushroom (marking)	HW1L-M3®-PS
	HW1L-A3®-PS
ø40 Jumbo Mushroom (marking)	HW1L-M4®-PS
	HW1L-A4®-PS

Package Quantity: 1

Package Quantity: 1			
	Contact Unit		
Shape	Contact	Part No.	
σπαρο	Configuration	(Ordering No.)	
	1NO	HW-CNP10Q0	
O	1NC	HW-CNP01Q0	
	1NO-1NC	HW-CNP11Q0	
	2N0	HW-CNP20Q0	
O	2NC	HW-CNP02Q0	
	2NO-2NC	HW-CNP22Q0	
	1NO	HW-CNP10Q0	
O	1NC	HW-CNP01Q0	
	1NO-1NC	HW-CNP11Q0	
	2N0	HW-CNP20Q0	
O	2NC	HW-CNP02Q0	
	2NO-2NC	HW-CNP22Q0	
	1NO	HW-CNP10Q0	
Ø	1NC	HW-CNP01Q0	
	1NO-1NC	HW-CNP11Q0	
	2N0	HW-CNP20Q0	
O	2NC	HW-CNP02Q0	
	2NO-2NC	HW-CNP22Q0	

Note) LED lamp is not supplied. When ordering contact units (illuminated) selected LED from below table.

LED lamp (package	LED lamp (package quantity:1)	
Rated Voltage	Part No. (Ordering No.)	
6V AC/DC	LSRD-6	
12V AC/DC	LSRD-1	
24V AC/DC	LSRD-2	
100/120V AC/DC	LSRD-H2	
200/220V AC	LSRD-M2	
230/240V AC	LSRD-M4	


Illuminated Pushbuttons Dimensions

All dimensions in mn

Round Flush


1 to 2 contacts

HW1L-□1P



3 to 4 contacts


HW1L-□1P



Round Extended


1 to 2 contacts

HW1L-□2P



3 to 4 contacts


HW1L-□2P



Round Extended with Full Shroud


1 to 2 contacts

HW1L-□F2P



3 to 4 contacts


HW1L-□F2P



Square Flush


1 to 2 contacts

HW2L-□1P



3 to 4 contacts

HW2L-□1P




Illuminated Pushbuttons Dimensions

All dimensions in mm

ø29 Mushroom


1 to 2 contacts

HW1L-□3P



3 to 4 contacts


HW1L-□3P



ø40 Jumbo Mushroom


1 to 2 contacts

HW1L-□4P




3 to 4 contacts

HW1L-□4P



Illuminated Pushbuttons Part No. Example

Assembled and sub-assembled unit



• For available assembled products, see table on page 17.

Operator unit HW1L - M 1 R - PS ①Bezel shape code 6 Button color code (see page 18) 1: Round 2: Square 3: Round Bezel 3 Button style code 1: Flush 20peration code 2: Extended M: Momentary F2: Round Extended with A: Maintained full Shroud 3: ø29mm Mushroom 4: ø40mm Mushroom

Contact unit (illuminated)

• LED lamps are not supplied.

LED lamp


Company of Company

H2:100/120V AC/D M2:200/220V AC M4:230/240V AC

Dual Pushbuttons without Pilot Light

Sub-Assembled

Dual pushbuttons can be purchased only as a sub-assembled product.



Without Pilot Light

	<pre></pre>				
		<nei< td=""><td>CI CIICC></td><td></td></nei<>	CI CIICC>		
Ope		Contact Co	nfiguration	<reference></reference>	
Operation	Button style	Top Button	Bottom Button	Assembled Part No	
		1N0	1NC	HW7D-B11P10016⑦	
	Flush–Flush	1NO	1NO	HW7D-B11P10106⑦	
	riusii—riusii	1NO-1NC	1NO-1NC	HW7D-B11P11116⑦	
Momentary		2N0	2NC	HW7D-B11P200260	
enta:		1NO	1NC	HW7D-B12P100167	
Flush–Extended		1NO	1NO	HW7D-B12P10106⑦	
	Flush-Extended	1NO-1NC	1NO-1NC	HW7D-B12P111160	
	2N0	2NC	HW7D-B12P200267		
		1N0	1NC	HW7D-B21P100160	
	Fluck Fluck	1N0	1N0	HW7D-B21P10106⑦	
Flush-Flush	1NO-1NC	1NO-1NC	HW7D-B21P111160		
		2N0	2NC	HW7D-B21P2002607	
Interlocking (*1)		1N0	1NC	HW7D-B22P10016⑦	
	Fluor Extended	1N0	1N0	HW7D-B22P10106⑦	
	Flush–Extended	1NO-1NC	1NO-1NC	HW7D-B22P11116⑦	
		2N0	2NC	HW7D-B22P20026⑦	

Sub-Assembled Ordering No.

HW7D-B11®⑦-PS HW7D-B21®⑦-PS	Operator Unit
HW7D-B12®⑦-PS HW7D-B21®⑦-PS	Part No. (Ordering No.)
HW7D-B21®⑦-PS	HW7D-B11®⑦-PS
	HW7D-B12⑥⑦-PS
LIMIZD DOG ® PC	HW7D-B21®⑦-PS
HM\D-R55@(\)-L2	HW7D-B22®⑦-PS

Package	Quantity:	1

Contact Unit		
Contact Configuration		Part No. (Ordering No.)
Top Button	Bottom Button	Ø
1NO	1NC	HW-CNP11
1NO	1NO	HW-CNP20
1NO-1NC	1NO-1NC	HW-CNP22
2N0	2NC	HW-CNP22N1
1NO	1NC	HW-CNP11
1NO	1N0	HW-CNP20
1NO-1NC	1NO-1NC	HW-CNP22
2N0	2NC	HW-CNP22N1


- *1) Interlock: Momentary operation. When one of the buttons is pressed, the other button cannot be operated. Do not operate top and bottom buttons at the same time. Operating the buttons at the same time may lead to malfunctions.
- For contact mounting position, see page 51.
- Specify a code in place of @@ in the Part No. See tables below

® Button Color Code

Code	
GR	Top Button Green Bottom Button Red
WB	Top Button White Bottom Button Black

⊘Button Legends Code

Code	
Blank	Blank
1	Top Button: I & ON / Bottom Button: O & OFF



Note) (2) can only be mounted with a dummy block.

Contact Configuration


Contact	Configurat	tion	Conta	ct Block	(Top Button Bottom Button			Button	Button																					
Top Button	Bottom Button	Code	Mounting Position	Contact		Nomal	Push	Nomal	Push	Position —Pushbutto Operation																					
1110	1110	1001	(1)	NO			•			oporation																					
1NO	1NC	1001	(3)	NC	;			•																							
4110	4110	4040	(1)	NC)		•																								
INU	1NO 1NO 1010 (3)		(3)	NO					•																						
	1NO-1NC	NO-1NC 1111 -		NONC	NO		•																								
1NO-1NC					NC	•																									
TINO-TING				NONC	NO				•																						
																										(3)	NUNC	NC			•
			(1)	2N0	NO		•																								
2N0	2NC	2002		ZINO	NO		•																								
ZINO	2110	2002		2NC	NC			•																							
			(3)	2110	NC			•																							

Contact block (1) is actuated by the top button. Contact block (3) is actuated by the bottom button.

Dual Pushbuttons with Pilot Light

Sub-Assembled

Dual pushbuttons can be purchased only as a sub-assembled product.



Without Pilot Light

Without Filot Eight							
			<reference< th=""><th>?></th></reference<>	? >			
0pe	Button Style	Contact Co	nfiguration	(Deference)			
Operation		Top Button	Bottom Button	<reference> Assembled Part No</reference>			
		1NO	1NC	HW7D-L11P1001PW6⑦			
	Fluck Fluck	1NO	1NO	HW7D-L11P1010PW6⑦			
	Flush-Flush	1NO-1NC	1NO-1NC	HW7D-L11P1111PW60			
l om		2N0	2NC	HW7D-L11P2002PW6⑦			
Momentary	Flush– Extended	1NO	1NC	HW7D-L12P1001PW6⑦			
3		1NO	1NO	HW7D-L12P1010PW6⑦			
		1NO-1NC	1NO-1NC	HW7D-L12P1111PW60			
		2N0	2NC	HW7D-L12P1010PW67			
		1NO	1NC	HW7D-L21P1001PW6⑦			
	Fluck Fluck	1NO	1NO	HW7D-L21P1010PW6⑦			
Inte	Flush-Flush	1NO-1NC	1NO-1NC	HW7D-L21P1111PW60			
rloc		2N0	2NC	HW7D-L21P2002PW6⑦			
Interlocking (*1)		1NO	1NC	HW7D-L22P1001PW6⑦			
(±)	Flush-	1NO	1NO	HW7D-L22P1010PW®⑦			
	Extended	1NO-1NC	1NO-1NC	HW7D-L22P1111PW@⑦			
		2N0	2NC	HW7D-L22P2002PW67			

Sub-Assembled Ordering No.

Package Quantity: 1

Operator Unit
Part No. (Ordering No.)
1
HW7D-L11PW®⑦-PS
HW7D-L12PW®⑦-PS
HW7D-L21PW®⑦-PS
HW7D-L22PW®⑦-PS

Contact Unit							
Contact Co	nfiguration	Part No. (Ordering No.)					
Top Button	Bottom Button	O					
1NO	1NC	HW-CNP11Q0					
1NO	1NO	HW-CNP20Q0					
1NO-1NC	1NO-1NC	HW-CNP22Q0					
2N0	2NC	HW-CNP22N1Q0					
1NO	1NC	HW-CNP11Q0					
1NO	1NO	HW-CNP20Q0					
1NO-1NC	1NO-1NC	HW-CNP22Q0					
2N0	2NC	HW-CNP22N1Q0					

- *1) Interlock: Momentary operation. When one of the buttons is pressed, the other button cannot be operated.
- Do not operate top and bottom buttons at the same time.

 Operating the buttons at the same time may lead to malfunctions.
- For contact mounting position, see page 52.
- \bullet Specify a code in place of $\circledcirc \ensuremath{\mathscr{D}}$ in the Part No. See tables below

Code	Rated Voltage	Code	Rated Voltage
Q2	6V AC/DC	QH2	100/120V AC/DC
Q3	12V AC/DC	QM	200/220V AC
Q4	24V AC/DC	QM4	230/240V AC

®Button Color Code

Code	
GR	Top Button Green Bottom Button Red
WB	Top Button White Bottom Button Black

7Button Legends Code

Code	
Blank	Blank
1	Top Button: I & ON / Bottom Button: O & OFF

Note) LED lamp is not supplied. When ordering contact units (illuminated) selected LED from below table.

LED lamp (Package Quantity: 1)							
Rated Voltage Part No. (Ordering No.)							
6V AC/DC	LSRD-6						
12V AC/DC	LSRD-1						
24V AC/DC	LSRD-2						
100/120V AC/DC LSRD-H2							
200/220V AC LSRD-M2							
230/240V AC	LSRD-M4						

Contact Block Mounting Position



Note) (2) can only be mounted with a full voltage adapter.


Dual Pushbuttons Dimensions

All dimensions in mm


Without Pilot Light

Flush-Flush

1 to 2 contacts




3 to 4 contacts




Flush-Extended

1 to 2 contacts




3 to 4 contacts




With Pilot Light

Flush-Flush

1 to 2 contacts




3 to 4 contacts




Flush-Extended

1 to 2 contacts



3 to 4 contacts




Dual Pushbuttons

Dual Pushbuttons Part No. Example


Assembled and sub-assembled unit

Assembled (without pilot light)



Тор	Bottom	Contact co	t configuration		
button	button button		Bottom button		
1NO	1NC	10	01		
1NO	1N0	10	10		
1NO-1NC	1NO-1NC	11	11		
2N0	2N0	20	02		

Operator unit (without pilot light)




Contact unit

HW- CN P 20 (see page 23)

Assembled (with pilot light)






ĺ	Тор	Bottom	Contact co	onfiguration		
١	button	button	Top button	Bottom button		
	1N0	1NC	10	01		
I	1N0	1NO	10	10		
I	1NO-1NC	1NO-1NC	11	11		
Ì	2N0	2N0	20	02		

DButton Legends Code 1:1 & ON / O & OFF ®Button color code GR: Top Button Green **Bottom Button Red** WB: Top Button White **Bottom Button Black**

> Q4: 24V AC/DC QH2: 100/120V AC/DC QM: 200-220V AC QM4: 220-240V AC

Operator unit (with pilot light)



Contact unit (for illuminated unit)

HW-CNP20Q0 (see page 24)

• LED lamps are not supplied.

LED Lamp

LSRD - 6 **⑤Rated Voltage code**

6 : 6V AC/DC H2 : 100/120V AC/DC : 12V AC/DC M2 : 200/220V AC : 24V AC/DC M4 : 230/240V AC

Selector Switches (Knob Operator)

Assembled



Package Quantity: 1

	1							Package Quantity.				
	No. of Positions	Contact				Operator Position		Cam	1 2			
Shape		Configuration (Code)	Mounting Position	Conta	act	1	2		Code	Maintained		
HW1S		1NO	(1)	NO	1		•			HW1S-2TP10	/	
		(10)	(3)	_		Dur	nmy			111110] /	
		1NC	(1)		_		— Dı		Dummy			HW1S-2TP01
		(01)	(3)	NC		•						
		1NO-1NC	(1)	NO			•			HW1S-2TP11	/	
	90° 2-position	(11)	(3)	NC		•			_			
	- position	2NO (20)	(1)	NO			•			HW1S-2TP20		
		- (-)	(3)	NO			•				/ !	
		2NO-2NC (22)	(1)	NONC	NO		•					
			(3)		NC	•			-	HW1S-2TP22		
				NONC	NO NC	•	•		1			
		Contact Configuration (Code)	Conta	act Block		_	ator Po	eition		Maintained 1 0 2	Spring return two-way	
			Mounting	Contact		Open	2101 1 0	Joilloii				
			Position			1	0	2				
		2N0 (20)	(1)	NO NO		•			_	HW1S-3TP20	HW1S-33TP20	
			(3)					•		11W10 311 20	11W10 3311 20	
		2NO-1NC	(1)	NONC	NO	•					/	
		(21N1)			NC		•		J	HW1S-2JTP30N1		
	45° 3-position	*☆	(3)	NO	NO			•				
	To a position		(1)	NONC	NO	•						
		2NO-2NC			NC					HW1S-3TP22		
		(22)	(3)	NONC	NO			•	-			
					NC				_		/	
			(1)	2N0	NO NO	•			-			
		4NO (40)			NO NO	•		-	-	HW1S-3TP40		
			(3)	2N0	NO NO			•	-		/	
					NO			•			V	

- On the contact configuration marked with *\pm\$ in the table above, the rated load switching current
 is reduced to a half of the related current of the contact block. The rated insulation voltage and the
 rated thermal current remain unchanged.
- On the contact configuration marked with ☆ in the table above, contacts may overlap when the operator position is changed.
- Knob operator: white indicator on black body
- Selector switches with 1 contact block contain 2 dummy blocks.
 Selector switches with 2 contact blocks contain 1 dummy block.
- Turn the operator to each position accurately.
 - For other contact configuration or operator position, select from sub-assembled units (page 27 to 28).

Contact Block Mounting Position





Note) (2) can only be mounted with a dummy block.


All dimensions in mm.


Dimensions

1 to 2 contacts









Selector Switches (Knob / Lever Operator) 2-Position

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 26 for available assembled products.



90° 2-position

Package Quantity: 1

50	2 position rackage qualitity. I												
		<	<reference< td=""><td>e> As</td><td>semble</td><td>d Part</td><td>No.</td><td></td><td>Operator</td><td>Unit Ordering No.</td><td colspan="3">Contact Unit</td></reference<>	e> As	semble	d Part	No.		Operator	Unit Ordering No.	Contact Unit		
z		Contact Block		Operator Position				Operator Position Code		Operator Position Code			
No. of Positions	Contact Configuration			Opera 1	2	SILION	Cam Code	Maintained 1 2	④ Operator type	Maintained 1 2 (90°)	Shape	Part No. (Ordering No.)	
sition	(Code)	Mounting Position Contact	Contact				Code	<reference></reference>	орегатог туре	Part No.		(Ordering No.)	
S				®	Ø			Assembled Part No.		(Ordering No.)			
	1NO (10)	(1)	NO	Dun	nmy			HW1S-2@P10	Knob			HW-CNP10	
	1NC	(1)			nmy			Operator Operator					
	(01)	(3)	NC	•			HW1S-2@P01	100		*	HW-CNP01		
	1NO-1NC (11)	1NO-1NC (1) NO •		HW1S-2@P11	Lever		V	HW-CNP11					
	2NO	(1)	NO		•			HW1S-2@P20	Operator			HW-CNP20	
	(20)	(3)	NO		•			11W13-2⊕120	300			TIW-CINF 20	
	2NC (02)	(1)	NC NC	•				HW1S-24P02			A	HW-CNP02	
	(02)	(1)	NO		•								
9	2NO-2NC	(2)	NC	•]	HW1S-2@22				HW-CNP22	
000	(22)	(3)	NO NO		•			11W13-2-22				TIW-GIVE ZZ	
12-6	<u> </u>	(4)	NC NC	•			_		HW1S-24-PS				
Sitio	3NO-1NC			•									
=	(31N1)		NO		•			HW1S-2@31				HW-CNP31	
		(5)	NO		•								
					•]						
					•			HW1S-2@40				HW-CNP40	
	(40)				_								
				•									
		(')		•				HW1S-2@03N2				HW-CNP03N2	
	(03N2)	(3)	NC	•									
	2NO-1NC	(1)	2NO NO		•								
	(21N1)	. ,	NO	•	•			HW1S-2@21N1				HW-CNP21N1	
90° 2-position	4NO (40) 3NC (03N2) 2NO-1NC	(1) (3) (4) (5) (1)	NO NO NO NO NO NC	•	•			HW1S-2⊕31 HW1S-2⊕40 HW1S-2⊕03N2 HW1S-2⊕21N1				HW-CNP31 HW-CNP40 HW-CNP03N2 HW-CNP21N1	

90° 2-position Reversed Cam

Package Quantity: 1

	·											
		<	Referen	ce> Asser	mbled Part	No.		Operator	Unit Ordering No.	Co	Contact Unit Part No. (Ordering No.)	
No. of Positions	Contact	Contact Block		Operator Position		Cam	Operator position code Maintained 1 2		Operator position code Maintained 1 2		Part No.	
	Configuration (Code)	Mounting Position	Contact	2	1	Code	<reference> Assembled Part No.</reference>	Shape	Part No. (Ordering No.)	Shape	** ** *	
90° 2-r	2NC	(1)	NC		•		HW1S-2J⊕TP02	Knob Operator	HW1S-2J⊕-PS		HW-CNP02	
-position	(02)	(3)	NC		•	J	HW15-2J⊕1P02	Lever Operator		O	NV-GIVEUZ	

[•] For part no. other than maintained position, see Part No. Example on page 29.

Note: Turn the operator to each position accurately.

@Operator Unit Code

Code	Operator style	Code	Operator style
T	Knob Operator	L	Lever Operator

[•] Specify an operator unit code in place of ④ in the Part No.

Selector Switches (Knob / Lever Operator) 3-Position

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 26 for available assembled products.



45° 3-position Package Quantity: 1

	<reference> Assembled Part No.</reference>								Operator Unit Ordering No.			ntact unit
No. of Positions	Contact Configuration (Code)	Conta Mounting Position	act Block Contact	1	ator Po	2	Cam Code	Operator position code Maintained 1 0 2 <reference></reference>	④ Operator type	Operator position code Maintained Part No.	Shape	Part No. (Ordering No.)
8				®		Ø		Assembled Part No.		(Ordering No.)		
	1NO-1NC (11)	(1)	NO NC	-				HW1S-3@P11	Knob Operator			HW-CNP11
	1NO-1NC (11N1)	(1)	NC NO			•		HW1S-3@P11N1		HW1S-3@-PS	0	HW-CNP11N1
	2N0 (20)	(1)	NO NO	•		•	_	HW1S-3@P20	Lever	HW15-3(4)-P5		HHW-CNP20
	2NC (02)	(1)	NC NC					HW1S-3@P02	Operator			HW-CNP02
	1NO-1NC (11N1) ★☆	(1)	NC NO		•	•	J	HW1S-3J@P11N1			O	HW-CNP11N1
	2NO-1NC	(1)	NONC NO	•	•	J HW1S-3J@P21N3		HW1S-3J@-PS		HW-CNP30N1		
45°	(21N3) ★☆	(3)	NO NO			•						
3-position	2NO-2NC	(1)	NONC NO	•	_			HW1S-3@P22N1				HW-CNP22N1
sition	(22)	(3)	NONC NO			•		111110 001 22111				TIW ON ZENT
	2NO-2NC	(1)	2NC NO					LINE O O DOON O				
	(22N2)	(3)	2NO NO			•		HW1S-3@P22N2				HW-CNP22N2
	4N0	4NO (1) 2NO NO •		HW1S-3@-PS								
	(40)	(3)	2NO NO • HW15	HW1S-3@P40				HW-CNP40				
	4NC	(1)	2NC NC									
	(04)	(3)	2NC NC					HW1S-3@P04				HW-CNP04

- On the contact configuration marked with ★ in the table above, the rated load switching current is reduced to a half of the related current of the contact block.
 The rated insulation voltage and the rated thermal current remain unchanged.
- On the contact configuration marked with ☆ in the table above, contacts may overlap when the operator position is changed.
- For part no. other than maintained position, see Part No. Example on page 29.
- \bullet Specify an operator unit code in place of $\ensuremath{\textcircled{4}}$ in the Part No.

@Operator Unit Code

Code	Operator style	Code	Operator style
T	Knob Operator	L	Lever Operator

Note: Turn the operator to each position accurately.

Contact Block Mounting Position




Note) (2) can only be mounted with a dummy block.

Selector Switches (Knob / Lever Operator)

Selector Switches Part No. Example

Assembled and sub-assembled unit

Assembled (Without Pilot Light)




① Operator position code

Maintained (9	0° 2-position)	Spring Return (60° 2-position)			
		Spring Return from Right			
1 2	2 1	1 -2			
Cam code: blank	Cam code: J	Cam code: blank			


Maintained (45° 3-position)	Spring Return (45° 3-position)								
	Spring return from right	Spring return from left	Spring return two-way						
1 0 2	1 0 2	1 2	1 0 2						
Cam code: Blank, J, or S									

• For available assembled products, see table on page 26.

Operator (Without Pilot Light)



Contact Unit



Key Selector Switches (Disc Tumbler Key)

Assembled



Package Quantity: 1

Name / Chane	No. of	Contact Configuration		act Block			perat ositio		Cam	Operator position code Maintained (90°)	, actuago quantity.
Name / Shape	Positions	(Code)	Mounting Position	Contact		1	2		Code	1 2	_
Disc Tumbler		1NO	(1)	NO			•			HW1K-2AP10 (Key removable in all positions)	
Key		(10)	(3)			Dun	nmy			HW1K-2BP10 (Key removable at left)	
HW1K		1NO-1NC	(1)				•			HW1K-2AP11 (Key removable in all positions)	
	90°	(11)	(3)			•				HW1K-2BP11 (Key removable at left)	
		2N0	(1)	NO			•			HW1K-2AP20 (Key removable in all positions)	
	2-position	(20)	(3)	NO	NO		•		_	HW1K-2BP20 (Key removable at left)	
	i Si		(1)	NONC	NO		•				
		2NO-2NC	(1)	NONC	NC	•				HW1K-2AP22N2 (Key removable in all positions)	
		(22)	(3)	NONC	NO		•			HW1K-2BP22N2 (Key removable at left)	
			(3)	NONC	NC	•					
$ \rightarrow \rangle$			Conto	tact Block		Operator				osition code	
(NC contact		Contact	Contact Diock			Position		Cam	Maintained	Spring return from right	
only)		Code	Mounting Position	Contact		1	0	2	Code	1 0 2	1 0 2
		2N0	(1)	NO		•				HW1K-3AP20 (Key removable in all positions)	
	45	(20)	(3)	NO	NO			•	_	HW1K-3BP20 (Key removable at left/center) HW1K-3DP20 (Key removable at center)	
	45° 3-position	1NO-1NC	(1)	NC			•			HW1K-3JBP11N1 (Key removable at left/center)	
	posi	(11N1)	(3)	NO				•	J	HW1K-3JGP11N1 (Key removable at left)	
	tion	2NO-2NC	(1)	NONC	NO NC	•	_		_		HW1K-31BP22 (Key removable at left/center)
		(22)	(3)	NONC	NO NC			•	_		HW1K-31GP22 (Key removable at left)
		2a-2b (22N2)	(1)	2NC	NC NC				_		HW1K-31BP22N2 (Key removable at left/center)
			(1)	2N0	NO NO			•	_		HW1K-31GP22N2 (Key removable at left)

Selector switches with 1 contact block contain 2 dummy blocks.
 Selector switches with 2 contact blocks contain 1 dummy block.

- Standard key number (231) is available for assembled products.
 *For numbers other than standard key numbers, contact IDEC.
 - For other contact configuration or operator position, select from sub-assembled units (page 31 to 32).

Key removal position

1 90° 2-position

⊕ 90 Z-position										
Key Retained Position (Cam code: blank)										
A: Key removable in all positions	B: Key removable at left									
1 2	0 0									

①②: Key removal position ①②: Key retained position

2 45° 3-position

© 40 0-position										
Key Retained Position										
A: Key removable in all positions	B: Key removable at left / center	D: Key removable at center	G: Key removable at left							
0 2	0 0 2	0 0 0	0 0							

①①②: Key removal position **①①②**: Key retained position Note: The key cannot be removed in a spring return position.

Contact Block Mounting Position



Note) (2) can only be mounted with a dummy block.

Pin tumbler keys can be purchased only as a sub-assembled product.

Key Selector Switches (Disc Tumbler Key / Pin Tumbler Key) 2-Position

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 30 for available assembled products.



90° 2-position Package Quantity: 1

			<refe< th=""><th>rence></th><th>Asse</th><th>mbled P</th><th>art No.</th><th>Operator</th><th>Unit Ordering No.</th><th colspan="2">Contact Unit</th></refe<>	rence>	Asse	mbled P	art No.	Operator	Unit Ordering No.	Contact Unit		
No.		Con	tact Blo	ck		perator		Operator position code		Operator position code		
of Po	Contact Configuration				1	Position 2	Cam Code	Maintained 1 2	③Key Operator	Maintained 1 2	Shape	Part No. (Ordering No.)
No. of Positions	(Code)	Mounting Position	Cont	tact	(2)	<u></u>	Code	<reference> Assembled Part No.</reference>	Туре	Part No. (Ordering No.)		(Ordering No.)
	1NO	(1)	N	0		•			Disc Tumbler	(Ordering No.)		
	(10)	(3)	_	_	Dur	nmy		HW1K-234P10	DISC IUIIIDIGI			HW-CNP10
	1NC	(1)	_	-	Dur	nmy		TIMAK O@@DO4	All and a second			HW-CNP01
	(01)	(3)	N		•			HW1K-234P01	A		*	HW-GNPUT
	1NO-1NC	(1)	N	-		•		HW1K-234P11			$-\mathcal{O}$	HW-CNP11
	(11)	(3)	NC •				11W1K-2@⊕111				THE OILL TE	
	2NO	(1)	N			•		HW1K-234P20	Pin Tumbler		HW-CNP20	
	(20) 2NC	(3)	NO NO	-	•	•						
	(02)	(3)			•		_	HW1K-234P02	All and the same of the same o			HW-CNP02
	(02)				NO	•						
	2NO-2NC	(1)	NONC	NC	•							
90°	(22)	(0)	NONO	NO		•		HW1K-234P22				HW-CNP22
2		(3) NO	NONC	NC	•				HW1K-2346-	HW1K-2346-PS		
2-position		(1) NONC	NO		•							
l ti	3NO-1NC	(1)	INUING	NO		•		HW1K-234P31				HW-CNP31
	(31)	(3)	NONC	NO		•		HWIK-209F31				TIW-ONF31
		(0)	110110	NC	•							
		(1)	2N0	NO		•						
	4NO	- '		NO		•		HW1K-234P40				HW-CNP40
	(40)	(3)	2N0	NO NO		•	_					
				NC	•	-						
	3NC	(1)	2NC	NC			_	HW1K-234P03N2				HW-CNP03N2
	(03N2)	(3)	NC	NC	•		-	IIWIK-Z@GFUSINZ				TIW-ON OSNZ
				NO	Ť	•						
	2NO-2NC	(1)	2N0	NO		•	\dashv	HW1K-234P21N1				HW-CNP21N1
	(21N1)	(3)	NO	NC	•							

- For part no. other than maintained position, see Part No. Example on page 33.
- Each selector key switch is supplied with two keys.
- Specify the key style in ③. ③Key type code

Code	Key Operator Shape
Blank	Disc tumbler
Р	Pin tumbler

• Specify the desired key removal position in 4.7 See page 33 Part No. Developent

Specify the key number in ⑥.

for details.

Key Selector Switches (Disc Tumbler Key / Pin Tumbler Key) 3-Position

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 30 for available assembled products.



45° 3-position Package Quantity: 1

<reference> Assembled Part No.</reference>									Operator Unit Ordering No.		Contact Unit		
No. c	Contact	Con	tact Blo	ck	Operator Position			Operator position code		Operator position code			
No. of Positions	Configuration	Mounting	ounting Contact		1	0	2	Cam Code	Maintained	③Key Operator Type	Maintained	Shape	Part No. (Ordering No.)
ions	(Godo)	Position		laci	®		Ø		<reference> Assembled Part No.</reference>		Part No. (Ordering No.)		
	1NO-1NC (11)	(1)	N N		•				HW1K-334P11	Disc Tumbler			HW-CNP11
	1NO-1NC (11N1)	(1)	N N	-			•		HW1K-334P11N1		1111141 0 @ BO	A	HW-CNP11N1
	2N0 (20)	(1)	N N	-	•		•	_	HW1K-334P20		HW1K-3@6-PS		HHW-CNP20
	2NC (02)	(1)	N N	-					HW1K-334P02	Pin Tumbler			HW-CNP02
	1NO-1NC (11N1) ★☆	(1)	N N			•	•	J	HW1K-3J34P11N1		HW1K-3J@®-PS		HW-CNP11N1
	2NO-1NC	(1)	NC		•	•		J	HW1K-3J34P11N3				HW-CNP30N1
4.	(211N3) ★☆	(3)	NO				•						
45° 3-position	2NO-2NC	(1)	NONC	NO NC	•				LINALY OF POO				LIIV ONDONIA
sition	(22)	(3)	NONC	NO NC			•		HW1K-334P22				HW-CNP22N1
	2NO-2NC	(1)	NONC	NC NC									
	(22N2)	(3)	NONC	NO NO			•		HW1K-334P22N2				HW-CNP22N2
	4NO	(1)	NONC	NO NO	•			_			HW1K-3@6-PS		
	(40)	(3)	NONC	NO			•		HW1K-334P40				HW-CNP40
		. ,		NO NC		_	•						
	4NC	(1)	NONC	NC		=			HW1K-334P04				HW-CNP04
	(04)	(3)	NONC	NC NC					TW 111-333(4)PU4				11VV-UNFU4

- On the contact arrangement marked with ★ in the table above, the rated load switching current is reduced to a half of the related current of the contact block. The rated insulation voltage and the rated thermal current remain unchanged.
- For models with ☆, contacts may overlap when the operator position is changed.
- For part no. other than maintained position, see Part No. Example on page 33.
- Each selector key switch is supplied with two keys.
- Specify the key style in 3.

3 Key type code

ency type code							
Code	Key Operator Shape						
Blank	Disc tumbler						
Р	Pin tumbler						

- \bullet Specify the desired key removal position in 4. $\cente{1}$ See page 33 Part No. Developent
- Specify the key number in ⑥.

for details.

Contact Block Mounting Position




Note) (2) can only be mounted with a dummy block.

Key Selector Switches (Disc Tumbler Key / Pin Tumbler Key)

Key Selector Switches Part No. Example

Assembled and sub-assembled unit

Assembled Part No. Example




Pin Tumbler Key Blank: Standard (500) -501 to -515 (non-standard)

Note: The key number is engraved on the key cylinder.

3-position

- A: Removable in all positions
- B: Removable in the left and center
- C: Removable in the right and center
- D: Removable in center only
- E: Removable in right and left
- G: Removable in left only
- H: Removable in right only

Operator unit



Pin Tumbler Key

Blank: Standard (500)

-501 to -515 (non-standard)

Note: The key number is engraved on the key cylinder.

3-position

- A: Removable in all positions
- B: Removable in the left and center
- C: Removable in the right and center
- D: Removable in center only
- E: Removable in right and left
- G: Removable in left only
- H: Removable in right only

Contact unit

HW- CN P 10 © Contact configuration code (see page 31, 32)

①Operator position code

Maintained (9	0° 2-position)	Spring Return (60° 2-position)
		Spring Return from Right
1 2	2 1	1 2
Cam code: blank	Cam code: J	Cam code: blank

Maintained (45° 3-position)	Spring Return (45° 3-position)						
	Spring return from right	Spring return from left	Spring return two-way				
1 0 2	1 0 2	1_0_2	1 0 2				
Cam code: Blank, J, or S		Cam code: blank					

• For available assembled products, see table on page 30.

4 Key removal position

90° 2-position / 60° 2-position

co 2 position, co 2 position								
Key Retained Position (Cam code: blank)								
A: Key removable in all positions	B: Key removable at left	C: Key removable at right						
0 2	0 0	2						

Key Retained Position (Cam code: J)									
A: Key removable in all positions	B: Key removable at left	C: Key removable at right							

45° 3-position

Key Retained Position										
A: Key removable	B: Key removable	C: Key removable	D: Key removable							
in all positions	at left / center	at center / right	at center							
0 0 2	0 0 0	0 2								
E: Key removable	G: Key removable	H: Key removable								
at right / left	at left_	at right								
0 0 2		2								

①①②: Key removal position
O●②: Key retained position
Note: The key cannot be removed in a spring return position.


Key Selector Switches (Pin Tumbler Key)

All dimensions in mm


Dimensions

Disc Tumbler Key

1 to 2 contacts




3 to 4 contacts




Pin Tumbler Key

1 to 2 contacts



3 to 4 contacts



Lever operator can be purchased only as a sub-assembled product.

Illuminated Selector Switches (Knob / Lever Operator) (LED)

Assembled




Package Quantity: 1

											•	donago duantity. I
			Contact Con	ifigurati	on Tabl	е				Functional S	Specifications	
Name / Shape	No. of Positions	Contact	Contact Block			Operator Position		Operating Voltage	Maintained	_	© Illumination Color Code	
		Configuration	Mounting Position	Contact		1	2		voitage			Color Code
		1NO-1NC	(1)	N	10		•			LIMAE ODIAOA®		
		(11)	(3) NC		IC	•	•			HW1F-2P11Q46		
		2N0	(1)	N	10		•			HW1F-2P20Q46		
	90° 2-position	(20) 2NO-2NC (22)	(3) NO •			24V AC/DC	HW1F-2F20Q4®		R (red)			
			(1)	(1) NONC			•		24V AG/DG			G (green) PW (pure white)
			(1)	INOING	NC	•				HW1F-2P22Q46		(50.5 11)
			(22)	NONC	NO		•			NW1F-2F22Q4®		
			(3)	INOING	NC	•						
			Contact Configuration Tab			1 Table				Operator p	osition code	
	No. of Positions	Contact	Contact Block		t Block Opera				Cam Code	Maintained	Spring return two-way	© Illumination
		Configuration	Mounting Position	Con	itact	1	0	2		1 0 2	1_0_2	Color Code
	45° 3-position	2N0	(1)	(1) NO		NO •		24V AC/DC	HW1F-3P20Q46	HW1F-33P20Q46	R (red)	
	40 0-position	(20)		N	10			•	24V AU/DU	11W11-3F20Q4®	11W11-33F20Q4®	G (green) PW (pure white

- \bullet Specify an illumination color code in place of \circledR in the Part No. \bullet Turn the operator to each position accurately.
- For other contact configuration or operator position, select from sub-assembled units. (page 36 to 37).

Contact Block Mounting Position



Note) (2) can only be mounted with a full voltage adapter.

Illuminated Selector Switches (Knob / Lever Operator) (LED) 2-Position

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 35 for available assembled products.



90° 2-position

Package Quantity: 1

	<reference> Assembled Part No</reference>								Operator Unit Contact Unit		it (Illuminated)
z							Operator position code	Operator position code			
No. of Positions	Contact Configuration	Contact Block			erator sition	Cam Code Maintained 1 2		Name / Shape	Maintained 1 2	Shape	Part No.
sitions	Comiguration	Mounting Position	Contact	1	2	Code	<reference> Assembled Part No.</reference>	опаре	Part No. (Ordering No.)		(Ordering No.)
	1NO	(1)	NO		•		HW1F-23P1056	Knob			HW-CNP10Q0
	(10)	(3)		Dum	-		ПW1F-2@F10@@	Operator			TIW-CINF TOQU
	1NC	(1)		Dum	my		HW1F-23P0156				HW-CNP01Q0
	(01)	(3)	NC	•			11W11 2@101@@				THE OIL OIGO
	1NO-1NC	(1)	NO		•		HW1F-23P1156	Lever Operator			HW-CNP11Q0
	(11)	(3)	NC	•	_	-		Operator			
	2N0 (20)	(1)	NO NO		•	-	HW1F-23P2056				HW-CNP20Q0
		(3)	NO NC	-	•	-				A	
	2NC (02)	(3)	NC	-		-	HW1F-23P0256			HW-CNP02Q0	
	(- /		l N		•	1		ł			
	2NO-2NC	(1)	I NIONIC L	C •	_	1					
99	(22)	(2)	l N	0	•	- H	HW1F-23P2256				HW-CNP22Q0
2-		(3)	NONC N	C •							
90° 2-position		(4)	NONO N	0	•	T —		H/	HW1F-236-PS		
l tion	3NO-1NC	(1)	NONC N	0	•		LINATE OF DOLER				LIM ONDO 100
	(31)	(2)	NONC N	0	•		HW1F-23P3156	NIF-23P3130		HW-CNP31Q0	
		(3)	NONC	C •							
		(1)	2NO N		•						
	4N0	('')	l N	0	•		HW1F-23P4056				HW-CNP40Q0
	(40)	(3)		0	•		1111111 2014000				THE ONE TOGO
		,		0	•	-		ļ			
	3NC	(1)		C •		-					LIIM ONDOONOO
	(03N2)	(2)		C • C		-	HW1F-23P03N256				HW-CNP03N2Q0
		(3)	NC N	_	•	-					
	2NO-2NC	(1)	2NO —	0	•	1	HW1F-23P21N156				HW-CNP21N1Q0
	(21N1)	(3)		C •		1	nwir-zorzinioo				HIVV-GINEZ HVIQU
		(5)	INO IN	∪ -		1					

• Specify an operator unit code in place of ③ in the Part No. ③Operator Unit Code

Code	Operator style
Blank	Knob Operator
L	Lever Operator

• Specify a rated voltage code in place of ⑤ in the Part No.

Code	Rated voltage	Code	Rated voltage
Q2	6V AC/DC	QH2	100/120V AC/DC
Q3	12V AC/DC	QM	200/220V AC
Q4	24V AC/DC	QM4	230/240V AC

• Specify an illumination color code in place of ⑥ in the Part No. R (red), G (green), Y (yellow), A (amber), S (blue), PW (pure white)

• For part no. other than maintained position, see Part No. Example on page 38.

Note) LED lamp is not supplied. When ordering contact units (illuminated) selected LED from below table.

LED lamp (package quantity:1)						
Rated Voltage	Part No. (Ordering No.)					
6V AC/DC	LSRD-6					
12V AC/DC	LSRD-1					
24V AC/DC	LSRD-2					
100/120V AC/DC	LSRD-H2					
200/220V AC	LSRD-M2					
230/240V AC	LSRD-M4					

Illuminated Selector Switches (Knob / Lever Operator) (LED) 3-Position

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 35 for available assembled products.

45° 3-position Package Quantity: 1

45	S 3-position Package quantity: 1 <reference> Assembled Part No Operator Unit Contact Unit (Illuminated)</reference>											
			<neiei< td=""><td>ence</td><td>> A55</td><td>emble</td><td>u rait ivu</td><td> '</td><td>·</td><td>Contact of</td><td>iit (iiiuiiiiiateu)</td></neiei<>	ence	> A55	emble	u rait ivu	 '	·	Contact of	iit (iiiuiiiiiateu)	
No. of Positions	Contact Configuration		tact Block	(erato ositior	1	Operator position code Maintained 1 0 2	Name / Shape	Operator position code Maintained 1 0 2	Shape	Part No. (Ordering No.)
itions	3	Mounting Position Contact 0 0 2		<reference> Assembled Part No.</reference>	- Chape	Part No. (Ordering No.)		(ordering No.)				
	1NO-1NC	(1)	NO		•			HW1F-33P1156	Knob			HW-CNP11Q0
	(11)	(3)	NC					nwir-soriioo	Operator			TIW ONI TIQO
	1NO-1NC (11N1)	(1)	NC NO				•	HW1F-33P11N156		HW1F-336-PS	O	HW-CNP11N1Q0
	2N0	(1)	NO		•			LIMAE 2@D20@@	Lever		100	HHW-CNP20Q0
	(20)	(3)	NO				•	HW1F-3③P20⑤⑥	Operator			TITIW-GNF 20Q0
	2NC (02)	(1)	NC NC					HW1F-33P0256				HW-CNP02Q0
	1NO-1NC	(1)	NC			•		HW1F-3J3P11N156			Q	HW-CNP11N1Q0
	(11N1) ★☆	(3)	NO				•	111111111111111111111111111111111111111				
	2NO-1NC (21N3) ★☆	(1)	I NIONIC: —	NO NC	•	•		HW1F-3J3P21N356		HW1F-3J36-PS		HW-CNP30N1Q0
4	(ZTNO) X A	(3)	NO •		•							
45° 3-position	2NO-2NC)-2NC (1) N	I NIONIC —	NO NC	•		-					HW-CNP22N1Q0
sition	(22)	(3)	I NIUNIC I	NO NC			•	HW1F-3③P22⑤⑥				
				NO	Ī				1			
	2NO-2NC	(1)	1 2NC ⊢	NC		4						
	(22N2)	(3)	2N0	NO			•	HW1F-33P22N256				HW-CNP22N2Q0
		(3)	ZINU	NC			•		ļ	LIMAE 2000 DC		
		(1)	2N() ⊢	NO	•					HW1F-336-PS	[
	4N0	(1)		NO	•			HW1F-33P4056				HW-CNP40Q0
	(40)	(3)	□ 2N(O	NO NO			•				"	
				NC					{			
	4NC	(1)	2N/C	NC		4		11114E 0@B04@@				LINA ONDO 400
	(04)	(3)	JONIC.	NC NC				HW1F-3③P04⑤⑥				HW-CNP04Q0
				INC					l			

 \bullet Specify an operator unit code in place of $\ensuremath{\mathfrak{I}}$ in the Part No. $\ensuremath{\mathfrak{I}}$ **3 Operator Unit Code**


Code	Operator style
Blank	Knob Operator
	Lever Operator

• Specify a rated voltage code in place of ⑤ in the Part No.

Code	Rated voltage	Code	Rated voltage
Q2	6V AC/DC	QH2	100/120V AC/DC
Q3	12V AC/DC	QM	200/220V AC
Q4	24V AC/DC	QM4	230/240V AC

• Specify an illumination color code in place of ® in the Part No. R (red), G (green), Y (yellow), A (amber), S (blue), PW (pure white)

Contact Block Mounting Position



Note) (2) can only be mounted with a LED module.

For part no. other than maintained position, see Part No. Example on page 38.
 Note) LED lamp is not supplied. When ordering contact units (illuminated) selected LED from below table.

LED lamp (package quantity:1)					
Rated Voltage	Part No. (Ordering No.)				
6V AC/DC	LSRD-6				
12V AC/DC	LSRD-1				
24V AC/DC	LSRD-2				
100/120V AC/DC	LSRD-H2				
200/220V AC	LSRD-M2				
230/240V AC	LSRD-M4				

Illuminated Selector Switches (Knob / Lever Operator) (LED)


All dimensions in mm

Dimensions

Knob Operator

1 to 2 contacts


3 to 4 contacts



Lever Operator


1 to 2 contacts

3 to 4 contacts



Illuminated Selector Switches Part No. Example

Assembled and sub-assembled unit



Selector Pushbuttons

Assembled



Package Quantity: 1

Name / Shape	Circuit	Contact		t Block	Left		(Right	Ring Operator	③ Button Color Code	
namo / enape	Code.	Configuration	Mounting Position	Contact	Normal	Push	Normal	Push	Part No. (Ordering No.)		
HW1R	n	D	2N0	(1)	NO		•				B (black)
	U	(20)	(3)	NO				•	HW1R-2DP203	G (green)	

- \bullet Specify a button color code in place of $\ensuremath{\mathfrak{D}}$ in the part No.
- When operating the pushbutton selector, do not turn the operator ring or the lock lever while the button is depressed.
 Otherwise the pushbutton selector may be damaged.


• For other circuit codes, select from sub-assembled units (page 40).


Contact Block Mounting Position



Note) (2) can only be mounted with a dummy block.


Dimensions





Selector Pushbuttons Part No. Example

Assembled and sub-assembled unit



Operator unit

HW1R - 2 A B - PS

①Circuit code

③Button color code (see page 40)


Contact unit

HW - CN P 10 ©Contact configuration code (see page 40)

Selector Pushbuttons

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 39 for available assembled products.



Sub-Assembled

<reference> Assembled Part No.</reference>											
Circuit Code	Contact Configuration		tact Blo	ck	Left			Right	Ring Operator	③ Button Color	
Code	(Code)	Mounting Position			Normal	Push	Normal	Push	Part No. (Ordering No.)	Code	
	1NO-1NC	(1) N		NO		•		•	HW1R-2AP113		
	(11)	(3)	N		•				IIW IN-ZAF I I ©		
	2N0	(1)	N			•		•	HW1R-2AP203		
A	(20)	(3)	N			•			IIWIII ZAI ZO®		
		(1)	2N0	NO		•					
	2NO-2NC			NO		•			HW1R-2AP22N13		
	(22)	(3)	2NC	NC	•					ZZIVI®	
		(4)	N	NC	•	•					
	2NO (20)	(1)	N			_			HW1R-2DP203		
	(20)	(1) NONC	NO		•				-		
D	2NO-2NC		NONC	NC	•					B (black)	
	(22)			NO	_				HW1R-2DP223		
	, ,	(3)	NONC	NC							
		(4)	NONO	NO		•				G (green) R (red) Y (yellow) S (blue)	
l E	2NO-2NC	(1)	NONC	NC					LINEAR OFFICE		
-	(22)★	(2)	(3) NONC	NO				•	HW1R-2EP223		
		(3)	INUINC	NC		1				W (white)	
		(1)	NONC	NO				•			
l _F	2NO-2NC	(1)	INOING	NC			•		HW1R-2FP223		
'	(22)★☆	(3)	NONC	NO		•			11W111-211 22®		
		(-)		NC	•						
		(1)	2NC	NC			•				
N	2NO-2NC			NC			•		HW1R-2NP22N23		
	(22N2)★☆	(3)	2N0	NO NO		•		•			
				NO NO		•	_	•			
		(1)	NONC	NO NC	•	•	•				
Т	2NO-2NC (22)			NO NO		•	•	Operation	HW1R-2TP223		
	(22)	(3)	NONC	NC	•			Blocked			
		L		NO							

Ordering No. Package Quantity						
Operator unit	Co	Contact unit				
Part No. (Ordering No.)	Contact Configuration (Code)	Part No. (Ordering No.)				
	1NO-1NC (11)	HW-CNP11				
HW1R-2A3-PS	2N0 (20)	HW-CNP20				
11W111 2A @ 10	2NO-2NC (22N1)	HW-CNP22N1				
	2N0 (20)	HW-CNP20				
HW1R-2D3-PS	2NO-2NC (22)	HW-CNP22				
HW1R-2E3-PS	2NO-2NC (22)	HW-CNP22				
HW1R-2F3-PS	2NO-2NC (22)	HW-CNP22				
HW1R-2N3-PS	2NO-2NC (22N2)	HW-CNP22N2				
HW1R-2T3-PS	2NO-2NC (22)	HW-CNP22				


- On the contact arrangement marked with ★ in the table above, the rated load switching current is reduced to a half of the related current of the contact block.
- The rated insulation voltage and the rated thermal current remain unchanged.
- \bullet For models with $\not \curvearrowright$, contacts may overlap when the operator position is changed.
- When operating the pushbutton selector, do not turn the operator ring or the lock lever while the button is depressed. Otherwise the pushbutton selector may be damaged.
- For contact mounting position, see page 51.

For Part No. (Ordering No.)/ mounting positions of contact units, see page 51.

Monolever Switches

Sub-Assembled

When ordering, specify the sub-assembled ordering no.



Sub-Assembled Ordering No.

Package Quantity: 1

Name / Shape	Positions	<reference> Assembled Part No.</reference>
HW1M Standard		HW1M-P1010-20
		HW1M-P2020-20
	0	HW1M-P0101-20
	2-position	HW1M-P0202-20
		HW1M-P0101-40
		HW1M-P0202-40
	4	HW1M-P1111-22N9
	4-position	HW1M-P2222-22N9
HW1M-L Interlocking		HW1M-LP1010-20
		HW1M-LP2020-20
		HW1M-LP0101-20
	2-position	HW1M-LP0202-20
		HW1M-LP0101-40
		HW1M-LP0202-40
		HW1M-LP1111-22N9
	4-position	HW1M-LP2222-22N9

On all mono-lever switches, the rated current (load switching)
current) is reduced to a half of the rated current of the contact
block. The rated insulation voltage and the rated thermal current
remain unchanged.

Оре	Operator unit				
Name / Shape	Part No. (Ordering No.)				
HW1M Standard	HW1M-P1010-PS				
April 2	HW1M-P2020-PS				
	HW1M-P0101-PS				
	HW1M-P0202-PS				
	HW1M-P0101-PS				
	HW1M-P0202-PS				
	HW1M-P1111-PS				
	HW1M-P2222-PS				
HW1M-L Interlocking	HW1M-LP1010-PS				
400	HW1M-LP2020-PS				
-6-	HW1M-LP0101-PS				
	HW1M-LP0202-PS				
	HW1M-LP0101-PS				
	HW1M-LP0202-PS				
	HW1M-LP1111-PS				
	HW1M-LP2222-PS				

Contact unit								
Shape	Contact	Part No.						
	Configuration	(Ordering No.)						
8	2NO (20)	HW-CNP20						
Ó	4NO (40)	HW-CNP40						
	2NO-2NC (22)	HW-CNP22						
8	2NO (20)	HW-CNP20						
O	4NO (40)	HW-CNP40						
	2NO-2NC (22)	HW-CNP22						

[•] For contact mounting position, see page 51.

For Part No. (Ordering No.)/ mounting positions of contact units, see page 51.

Monolever Switches

Contact Configuration

2-position (Right/Left)

1 3 3 7									
Contact		ntact lock		Lever Operator Position					
Code	Mounting Position	Contact Left Center				Right			
00	(1)	0	•						
20	(3)	N	0			•			
	(1)	2N0	NO	•					
40	(1)	ZINU	NO	•		•			
40	(3)	2N0	NO			•			
	(3)	ZINU	NO			Right			

2-position (Up/Down)

Contact	Contact Lever Operate Block Position					
Code	Mounting Position	Contact		Down	Center	Up
	(1) NO)	•		
	(3)	NO				•
00	(1)	2N0	NO	•		
20	(1)	ZINU	NO	•		
	(3)	2N0	NO			•
	(3)	2110	NO			•

Contact	Contact Block				l	ever 0- Posi		r
Code	Mounting Position	Contact		Down	Left	Center	Up	Right
	(1)	NONC	NO		•			
	(1)	NONC	NC					•
22	(3)	NONC	NO				•	
	(3)		NC	•				

Contact Block Mounting Position



Note) (2) can only be mounted with a dummy block.

Note) The lever operator of the interlocking type HW1M-L is locked only in the center position. Pull on the interlocking lever before operating the lever up/down/right/left.


Monolever Switches Part No. Example

Assembled and sub-assembled unit

Assembled Part No. Example HW1M-L P 1 0 1 0 - 20 3Contact configuration ①Model HW1M: Standard code HW1M-L: Interlocking Select a required contact operation at each lever 2 Lever operation mode operator position from Order of Entry the contact arrangement Up - Right - Down - Left charts above and specify 1: Maintained the Contact Code. 2: Spring returned

• For available assembled products, see table on page 41.

Operator unit




© Contact configuration code
Select a required contact
operation at each lever
operator position from the
contact arrangement charts
above and specify the


Contact Code.

Dimensions


0: Blocked

Standard





Interlocking Panel Thickness 0.8 to 6 70 (3 or 4 blocks) 72



Short Body Pilot Lights

Assembled



Package Quantity: 1

Name / Shape	Operating Voltage	Part No. (Ordering No.)	① Lens Color Code
Extended (Dome)	6V AC/DC	HW1P-2JPQ2①	R (red)
HW1P	12V AC/DC	HW1P-2JPQ3①	G (green)
	24V AC/DC	HW1P-2JPQ4①	Y (yellow) A (amber)
	100/120V AC/DC	HW1P-2JPRH2①	S (blue)
	200/240V AC/DC	HW1P-2JPCM2①	PW (Pure white)
Square Flush	6V AC/DC	HW2P-1JPQ2①	R (red)
HW2P	12V AC/DC	HW2P-1JPQ3①	G (green)
	24V AC/DC	HW2P-1JPQ4①	Y (yellow) A (amber)
S	100/120V AC/DC	HW2P-1JPRH2①	S (blue)
	200/240V AC/DC	HW2P-1JPCM2①	PW (Pure white)


- Built-in BA9S base LED lamp. See page **57** for LED Lamps.
- For square flush pilot lights, legends and symbols can be engraved on marking plates, or printed film can be inserted. For details on marking plates or film, see page 63. Engraving and films must be prepared by the customer.
- \bullet Specify a lens color code in place of $\ensuremath{\textcircled{1}}$ in the Part No.


Short Body Pilot Lights

Dimensions All dimensions in mm.


Extended (Dome)

6V, 12V, 24V AC/DC







100/120V AC/DC, 200/240V AC



Square Flush 6V, 12V, 24V AC/DC

X2





IDEC

Illuminated / Non-Illuminated Buzzers

Easy installation of buzzers and lamps

- Short, 19.7 mm depth behind panel.
- Buzzer and lamp functions are integrated. (Illuminated buzzers)
- IP65 waterproof from the front of the panel
- Installing an optional terminal rubber boot upgrades the terminal's waterproof characteristics to IP54 without the need to use a rear



• See website for details on approvals and standards.



Name / Shape	Part No. (Ordering No.)	Illumination Color	Sound Type	Package Quantity	Dimensions (All dimensions in mm.)
Illuminated Buzzer	HW1Z-P1F2PQ4R	Red	Intermittent	1	Gasket Locking Ring Panel Thickness 0.8 to 6
	HW1Z-P1F2PQ4Y			1	
Non-Illuminated Buzzer	HW1Z-2PQ4B	_	Steady		0.5
	HW1Z-F2PQ4B	_	Intermittent	ı	19.7 17.6

[•] See page 54 for details on terminal rubber boot.


Specifications and Ratings

Rated Insu	lation Voltage	30V			
Rated Volta	age	12 to 24V DC			
Voltage Ra	nge	10.8 to 26.4V DC			
Rated Curre	ent (effective value)	Illuminated: 18mA (24V DC), 8mA (12V DC) Non-Illuminated (Steady sound): 9mA (24V DC), 4mA (12V DC) (Intermittent sound): 7mA (24V DC), 3mA (12V D			
Inrush Cur	rent	100mA maximum			
	Sound Pressure (of HW1Z itself) (at 25°C)	90dB min. at 0.1m (24VDC) 70dB min. at 1m (24V DC, equivalent value) 84dB min. at 0.1m (12V DC) 64dB min. at 1m (12VDC, equivalent value)			
Buzzer	Sound Frequency (at 25°C)	2,200 to 2,450Hz			
	Sound Type	Illuminated: Intermittent Non-Illuminated: Steady/Intermittent			
	Intermittent Cycle (at 25°C)	105 cycles/minute approx. (1.75Hz approx.)			
Illumination	Illumination Type	Flashing			
illullillation	Flash Cycle (at 25°C)	105 cycles/minute approx. (1.75Hz approx.)			
Operating	Temperature	-20 to +50°C (no freezing)			
Operating	Humidity	20 to 85% RH (no condensation)			
Storage Te	mperature	-30 to +80°C (no freezing)			
Insulation	Resistance	100 MΩ minimum (500V DC megger)			
Dielectric S	Strength	Between live and earthed metal parts: 1000 AC, 1 minute			
Vibration F	Resistance	Damage limits: 5 to 55Hz, amplitude 0.5 mm Operating extremes: 5 to 55Hz, amplitude 0.5 mm			
Shock Res	iotopoo	Operating extremes: 100 m/s ²			
SHOCK NES	isiance	Damage limits: 1,000 m/s ²			
Degree of Protection Panel front Terminal		IP65 (IEC60529)			
		IP40 (IEC 60529) IP54 (with terminal rubber boot) (IEC 60529)			
Terminal Style		Push-in terminal			
Applicable Wire		Solid wire/ferrule (without insulation cover): 0.2 to 1.5 mm², AWG24-16 Ferrule (with insulation cover): 0.2 to 0.75 mm², AWG24-18			
Weight (ap	prox.)	17g			

Dimensions

All dimensions in mm.

With terminal rubber boot



- *2: The bellows must be 17 to 22mm long after installing the terminal rubber boot.
- *3: Maintain a cable angle of 45° max. to the HW1Z axis


Terminal Arrangement (botom view)





X1 and X2 have no polarity

Mounting Hole Layout



3.2 +0.2 hole is for anti-rotation. Not required when nameplate/anti-rotation is not used.

Instructions for Illuminated / Non-illuminated buzzers: see page 66

Emergency Stop Switches

Emergency Stop Switches

- Direct opening action (IEC 60947-5-5; 5.2, IEC 60947-5-1; Annex K)
- Safety lock mechanism (IEC 60947-5-5; 6.2)
- Degree of Protection IP65 (IEC 60529)











• See website for details on approvals and standards.


Specifications

•			
Operating Temperature		-25 to +60°C (no freezing)	
Operating Humidity		45 to 85% RH (no condensation)	
Storage Ter	mperature	-40 to +80°C (no freezing)	
Minimum F Direct Oper	orce Required for ning Action	80N	
Minimum Op Required for	erator Stroke Direct Opening Action	5.5mm	
Maximum (Operator Stroke	10.0mm	
Contact Re	sistance	50 mΩ maximum (initial value)	
Insulation F	Resistance	100 MΩ minimum (500V DC megger)	
Dielectric Strength		Between live and dead parts: 2500V AC, 1 minute Between terminals of different poles: 2500V AC, 1 minute Bet ween terminals of the same poles: 2500V AC, 1 minute	
Vibration	Damage limits	10 to 500 Hz, Amplitude 0.35 mm, Acceleration 50m/s ²	
Resistance	Operating extremes	10 to 500 Hz, Amplitude 0.35 mm, Acceleration 50m/s ²	
Shock Resi	otonoo	Damage limits: 1,000 m/s2	
SHOCK RESI	Stance	Operating extremes: 150 m/s2	
Operation F	requency	900 operations/hour	
	Mechanical	Single contact block: 100,000 operations minimum Double contact block: 50,000 operations minimum	
Life Electrical		Single contact block: 100,000 operations minimum Double contact block: 50,000 operations minimum (at 900 operations/h, duty ratio 40%)	
Degree of Protection		IP65 (IEC 60529), UL Type 4X	
Short-circu	it Protection	250V/10A fuse (Type aM IEC 60269-1/IEC 60269-2)	
Weight (approx.)		51g (HW1B-V4P02) 67g (HW1B-V4P04) 48g (HW1B-Y2P02)	



Mounting Hole Layout

All dimensions in mm.



Minimum Mounting Centers for HW1B (emergency stop switch)

	Vertical Spacing	Horizontal Spacing
HW1B-V3 HW1B-V4 HW1B-Y2	50 mm minimum	50 mm minimum
HW1B-V5	60 mm minimum	60 mm minimum

 The minimum mounting centers of HW1B (pushbuttons) and each HW series emergency stop switches are shown. For other button shapes, refer to the dimensions and take wiring and operation of switches into consideration.

Nameplate (for ø22 mm Emergency Stop Switches)

Package Quantity: 1

Shape	Legend	Part No.	Ordering No.	Remarks
	(blank)	HWAV-0-Y	HWAV-0-Y	HWAV-27-Y Nameplate color: yellow Legend color: black Panel thickness: 0.8 to 4.5 mm Material: Polyamide
	EMERGENCY STOP	HWAV-27-Y	HWAV-27-Y	Note) Cannot be used on ø60 mushroom pushlock turn reset switches. Use a nameplate exclusive for ø60 mushroom e-stop. See XW series catalog.

• "EMERGENCY OFF" and white (blank) nameplates available. See website or catalog for SEMI Emergency off (EMO) switches and Stop switches.

Note) For machinery subject to ISO/IEC standards such as machine tools and food machinery, in compliant with the revised ISO13850, it is not recommended to display texts or symbols such as EMERGENCY STOP on the actuator or nameplate of an emergency stop device.

Emergency Stop Switches

Assembled



Package Quantity: 1

		Package Quantity: 1
Name / Shape	Contact Configuration	Part No. (Ordering No.)
ø29mm Mushroom Pushlock Turn Reset HW1B-V3	1NC	HW1B-V3P01R
	1NO-1NC	HW1B-V3P11R
	2NC	HW1B-V3P02R
	3NC	HW1B-V3P03N2R
	1NO-1NC	HW1B-V3P22R
	4NC	HW1B-V3P04R

Name / Shape Configuration (Ordering No.) ø40mm 1NC HW1B-V4P01R Mushroom Pushlock Turn Reset HW1B-V4 1NO-1NC HW1B-V4P11R 2NC HW1B-V4P02R 3NC HW1B-V4P03N2R 1NO-1NC HW1B-V4P22R 4NC HW1B-V4P04R


Package Quantity: 1

- Pushlock turn reset Button is maintained when pressed and is reset when turned clockwise.
- Emergency stop switches with 1 contact block contain 2 dummy blocks. Pushbuttons with 2 contact block contains 1 dummy block.
- For other specifications, select from sub-assembled units (page 48).

Part No. Example

Assembled and sub-assembled unit


Assembled Part No. Example



• For available assembled products, see table above.

Note

Sub-assembled operator unit



Sub-assembled contact unit

HW- CN P <u>10</u> ③Contact configuration code Note) When choosing sub-assembled 01: 1NC push-pull operators, only up to 2 11: 1NO-1NC contacts can be used. 02: 2NC 12N1: 1NO-2NC • For emergency stop purposes, these switches must contain at least one NC contact block. 03N2: 3NO 2NO-2NC 22: 04: 4NC

IDEC

Emergency Stop Switches

Sub-Assembled

When ordering, specify the sub-assembled ordering no. See page 47 for available assembled products.



Pushlock Turn Reset

<Reference> Contact Button Color Code Name / Shape Assembled Configuration Part No. HW1B-V3P01@ ø29mm Mushroom 1NC 1NO-1NC HW1B-V3P11@ 2NC HW1B-V3P02@ R (red) 1NO-2NC $HW1B\text{-}V3P12N1 \\ \textcircled{4}$ Y (yellow) 3NC HW1B-V3P03N24 2NO-2NC HW1B-V3P224 4NC HW1B-V3P04@ ø40mm Mushroom 1NC HW1B-V4P01@ HW1B-V4 1NO-1NC HW1B-V4P11@ 2NC HW1B-V4P024 R (red) 1NO-2NC HW1B-V4P12N1@ Y (yellow) 3NC HW1B-V4P03N24 2NO-2NC HW1B-V4P224 4NC HW1B-V4P044 1NC HW1B-V5P01@ ø60mm Mushroom HW1B-V5 1NO-1NC HW1B-V5P11@ 2NC HW1B-V5P024 R (red) 1NO-2NC HW1B-V5P12N4 Y (yellow) 3NC HW1B-V5P03N24 2NO-2NC HW1B-V5P224 4NC HW1B-V5P044

 Pushlock turn reset – Button is maintained when pressed and is reset when turned clockwise.

Sub-assembled Ordering No. Pushlock Turn Reset

Package Quantity: 1

Operate	or Unit		Contact Unit	
Name / Shape	Part No. (Ordering No.)	Shape	Contact Configuration	Part No. (Ordering No.)
ø29mm Mushroom			1NC	HW-CNP01
		*	1NO-1NC	HW-CNP11
			2NC	HW-CNP02
	HW1B-V34-PS		1NO-2NC	HW-CNP12N1
			3NC	HW-CNP03N2
		\mathcal{O}	2NO-2NC	HW-CNP22
			4NC	HW-CNP04
ø40mm Mushroom		1N0-11 2NC 1N0-2l 3NC 2N0-2l	1NC	HW-CNP01
			1NO-1NC	HW-CNP11
			2NC	HW-CNP02
	HW1B-V4@-PS		1NO-2NC	HW-CNP12N1
			3NC	HW-CNP03N2
			2NO-2NC	HW-CNP22
			4NC	HW-CNP04
ø60mm Mushroom			1NC	HW-CNP01
			1NO-1NC	HW-CNP11
			2NC	HW-CNP02
	HW1B-V54-PS		1NO-2NC HW-CNP12N	HW-CNP12N1
			3NC	HW-CNP03N2
		\mathcal{O}	2NO-2NC	HW-CNP22
			4NC	HW-CNP04

Specify a button color code in place of (a) in the Part No. R (red), Y (yellow)
 Note) Y (yellow) cannot be used as a emergency stop switch by EN standards.

Push Pull

Pusii Puii						
Name / Shape	Contact Configuration	<reference> Assembled Part No.</reference>	Button Color Code			
ø40mm Mushroom HW1B-Y2	1NC	HW1B-Y2P014				
	1NO-1NC	HW1B-Y2P114	R (red) Y (yellow)			
	2NC	HW1B-Y2P02@				

 Push-Pull – 2-position switches with button maintained in both depressed and reset positions.

Push Pull

rusii ruii	
Operate	or Unit
Name / Shape	Part No. (Ordering No.)
ø40mm Mushroom	
	HW1B-Y2@-PS

Package Quantity: 1

	Contact Unit							
Sha	ipe	Contact Configuration	Part No. (Ordering No.)					
	8	1NC	HW-CNP01					
		1NO-1NC	HW-CNP11					
		2NC	HW-CNP02					

Specify a button color code in place of ④ in the Part No. R (red), Y (yellow)
 Note) Y (yellow) cannot be used as a emergency stop switch by EN standards.
 Note) Only up to 2 contacts can be used for push-pull switches.

For Part No. (Ordering No.)/ mounting positions of contact units, see page 51.


Emergency Stop Switches Dimensions


All dimensions in mm

DimensionsAll dimensions in mm.


ø29mm Mushroom Pushlock Turn Reset HW1B-V3


1 to 2 contacts






3 to 4 contacts







ø29mm Mushroom Pushlock Turn Reset HW1B-V4


1 to 2 contacts






3 to 4 contacts






ø60mm Mushroom Pushlock Turn Reset HW1B-V5

1 to 2 contacts





3 to 4 contacts



ø40mm Mushroom Push Pull (2-position) HW1B-Y2

1 to 2 contacts





Nameplates All dimensions in mm

When ordering, specify the Ordering No.

I	Description	Material	Part No.	Ordering No.	Package	Dimensions (mm)
	Legend				Quantity	
HWAM	Order marking plate	Plastic (black)	HWAM	HWAM	1	HWNP-□ marking plate (sold separately) is necessary. 1
IIWAW	(round) separately.	riadic (black)	IIWAWI	HWAMPN10	10	R14.9 14.9 15.5 1.5 1.5 1.5 1.5 1.5 1.5 1.5 1.5 1.
						HWNP-□ marking plate (sold separately) is necessary.
HWAQ	Order marking plate	Plastic (black)	HWAO	HWAQ	1	(Marking Plate)
HWAQ	(square) separately.	Flasiic (Diack)	HWAQ	HWAQPN10	10	8 R14.9 14.9 1.1 1.9 1.1 1.1
НМУС	Plank	Diactic (black)	HWAS-0	HWAS-0	1	1.6
HWAS	Blank	Plastic (black)	пwa5-U	HWAS-0PN10	10	

[•] Nameplates cannot be used on HW series control stations (HW1X).

Marking Plates for HWAM/HWAQ

When ordering, specify the Ordering No.

Description	Material	Part No.	Ordering No.	Package Quantity	Dimensions (mm)
LIMAID	Aluminum (black) Thickness = 1.0mm		HWNP-□	1	White legend on black background. Engraving area: W25×H7
HWNP		HWNP-□	HWNP-□PN10	10	≃ <u>√</u> 27 → ≃ 27 → 1

 $[\]bullet$ Specify a legend code in place of \square in the Ordering No.

Legends

Code	Legend
0	(blank)
1	ON
2	0FF
3	START
4	STOP STOP
31	OFF-ON
35	HAND-AUTO
53	HAND-OFF-AUTO

[•] See page 63 for how to install nameplates/marking plates, and how to remove marking plates.

Contact Unit

Contact Unit Part No. / Contact Configuration

Package Quantity: 1

Shape / Contact Block Mounting Position



(1)



Note) (2) can only be mounted with a dummy block.

3 to 4 contacts

			1 to 2 contacts	0 10 4 00111	1010
Contact Configuration (Code)	Part No. (Ordering No.)	Mounting Position	Contact	Contact Configuration (Code)	F
4110		(1)	1NO	ano l	
1NO (10)	HW-CNP10	(2)	Dummy	3N0 (30N1)	HW
(10)		(3)	Dummy	(30141)	
4110		(1)	Dummy	_	
1NC (01)	HW-CNP01	(2)	Dummy	3NC (03N2)	НΝ
(01)		(3)	1NC	(03142)	
		(1)	1NO] ,,,,, ,,,,,	
1NO-1NC (11)	HW-CNP11	(2)	Dummy	1NO-2NC (12N1)	НΝ
(11)		(3)	1NC	(12111)	
	HW-CNP11N1	(1)	1NC		
1NO-1NC (11N1)		(2)	Dummy	1NO-3NC	Н۷
(11111)		(3)	1NO	(13)	
	HW-CNP20	(1)	1NO		
2N0 (20)		(2)	Dummy	2NO-1NC	Н۷
(20)		(3)	1NO	(21N3)	
	HW-CNP02	(1)	1NC		
2NC		(2)	Dummy	3NO-1NC	НΝ
(02)		(3)	1NC	(31)	
		(1)	1NO-1NC	4110 0110	
2NO-2NC (22)	HW-CNP22	(2)	Dummy	1NO-3NC	Н۷
		(3)	1NO-1NC	(13)	
2NO-2NC (22N1)		(1)	2N0		
	HW-CNP22N1	(2)	Dummy	4N0	НΝ
		(3)	2NC	(40)	
2112 2115		(1)	2NC	400	
2NO-2NC	HW-CNP22N2	(2)	Dummy	4NC (04)	НΝ
(22N2)		(3)	2N0	(04)	

		1	
Contact Configuration (Code)	Part No. (Ordering No.)	Mounting Position	Contact
2112		(1)	2N0
3NO (30N1)	HW-CNP30N1	(2)	Dummy
(30141)		(3)	1NO
0110		(1)	2NC
3NC (03N2)	HW-CNP03N2	(2)	Dummy
(03142)		(3)	1NC
,,,,,		(1)	1NO-1NC
1NO-2NC (12N1)	HW-CNP12N1	(2)	Dummy
(12111)		(3)	1NC
4110 0110		(1)	1NO-1NC
1NO-3NC	HW-CNP13	(2)	Dummy
(13)		(3)	2NC
0110 4110		(1)	1NO-1NC
2NO-1NC (21N3)	HW-CNP21N3	(2)	Dummy
(Z1N3)		(3)	1NO
0110 4110		(1)	2N0
3NO-1NC (31)	HW-CNP31	(2)	Dummy
(31)		(3)	1NO-1NC
1110 0110		(1)	1NO-1NC
1NO-3NC (13)	HW-CNP13	(2)	Dummy
(13)		(3)	2NC
4110		(1)	2N0
4NO	HW-CNP40	(2)	Dummy
(40)		(3)	2N0
4110		(1)	2NC
4NC	HW-CNP04	(2)	Dummy
(04)		(3)	2NC

2N0


[•] Contact unit includes a contact block, connecting unit.

[•] Switches with 1 contact block contain 2 dummy blocks. Switches with 2 contact blocks contain 1 dummy block.


Contact Unit

Contact Unit (illuminated) Part No. / Contact Configuration

Package Quantity: 1







3 to 4 contacts

Note) (2) can only be mounted with a dummy block.

Full voltage adapter

1NO-1NC

2N0

Full voltage adapter

2NC

2NC

Full voltage adapter

2N0

Contact Mounting Configuration (Code) Part No. (Ordering No.) Contact Position 1N0 (1) 1N0 HW-CNP10Q0 Full voltage adapter (2) (10)(3) Dummy (1) Dummy 1NC HW-CNP01Q0 Full voltage adapter (2) (01) 1NC (3)1N0 (1) 1NO-1NC HW-CNP11Q0 Full voltage adapter (2)(11) (3)1NC 1NC (1) 1NO-1NC HW-CNP11N1Q0 Full voltage adapter (2) (11N1)(3)1N0 (1) 1N0 2N0 HW-CNP20Q0 (2) Full voltage adapter (20)(3) 1N0 (1) 1NC 2NC Full voltage adapter HW-CNP02Q0 (2) (02)1NC (3) 1NO-1NC (1)

HW-CNP22Q0

HW-CNP22N1Q0

HW-CNP22N2Q0

Contact Configuration (Code)	Part No. (Ordering No.)	Mounting Position	Contact
3NO		(1)	2N0
3NO (30N1)	HW-CNP30N1Q0	(2)	Full voltage adapter
(SUNT)		(3)	1NO
ONO		(1)	2NC
3NC (03N2)	HW-CNP03N2Q0	(2)	Full voltage adapter
(03142)		(3)	1NC
4110 0110		(1)	1NO-1NC
1NO-2NC (12N1)	HW-CNP12N1Q0	(2)	Full voltage adapter
(12111)		(3)	1NC
4110 0110		(1)	1NO-1NC
1NO-3NC (13)	HW-CNP13Q0	(2)	Full voltage adapter
(13)		(3)	2NC
0110 4110		(1)	1NO-1NC
2NO-1NC (21N3)	HW-CNP21N3Q0	(2)	Full voltage adapter
(Z 1145)		(3)	1NO
010 410		(1)	1NO
3NO-1NC (31)	HW-CNP31Q0	(2)	Full voltage adapter
(31)		(3)	1NO-1NC
4110 0110		(1)	1NO-1NC
1NO-3NC (13)	HW-CNP13Q0	(2)	Full voltage adapter
(10)		(3)	2NC
4110		(1)	2N0
4NO (40)	HW-CNP40Q0	(2)	Full voltage adapter
(40)		(3)	2N0
4110		(1)	2NC
4NC (04)	HW-CNP04Q0	(2)	Full voltage adapter
(04)		(3)	2NC

(3) • Contact unit (illuminated) includes a contact block, full voltage adapter, and connecting unit.

(2)

(3)

(1)

(2)

(3)

(1)

(2)

• Switches with 1 contact block contain 2 dummy blocks. Switches with 2 contact blocks contain 1 dummy block.

Note) LED lamp is not installed. When ordering a contact unit (illuminated), select a LED lamp from below.

LED lamp (package quantity:1)					
Rated Voltage Part No. (Ordering No					
6V AC/DC	LSRD-6				
12V AC/DC	LSRD-1				
24V AC/DC	LSRD-2				
100/120V AC/DC	LSRD-H2				
200/220V AC	LSRD-M2				
230/240V AC	LSRD-M4				

2NO-2NC

(22)

2NO-2NC

(22N1)

2NO-2NC

(22N2)

Accessories All dimensions in mm

	When ordering, specify the Ordering No.							
	Name / Shape	Material	Part No.	Ordering No.	Package Quantity	Remarks		
	Locking Ring Wrench	Metal (nickel-plated brass) Weight: approx. 150g	MW9Z-T1	MW9Z-T1	1	Used to tighten the locking ring when installing the HW switch onto a panel. 110		
Tool	Lamp Holder Tool	Nitrile rubber (black)	OR-55	OR-55	1	Used to install and remove the LED lamps. See page 60 for how to install. A : BA9S OR-55 B See page 60 for how to install. OR-55 See page 60 for how to install. OR-55 See page 60 for how to install.		
Anti-	rotation Ring	Ring: polyamide Gasket: nitril rubber	HW9Z-RL	HW9Z-RLPN10	10	Used to prevent the operator from turning. Generally used when using no nameplates on selector switches and pushbutton selectors. TOP 1.5 TOP 1.7 1.7 1.7 1.7 1.7 1.7 1.7 1.		
Rubb	er Mounting Hole Plug	Nitril rubber (black)	OB-31	OB-31PN05	5	Degree of protection: IP65 (round hole), IP40 (with anti-rotation function) Output Degree of protection: IP65 (round hole), IP40 (with anti-rotation function) Output Degree of protection: IP65 (round hole), IP40 (with anti-rotation function)		
Mounting Hole Plug		Plug: Metal (Zinc diecast) Locking nut: Polyamide Gasket: Nitrile rubber	LW9Z-BM	LW9Z-BM	1	Degree of protection: IP66 (round hole), IP40 (with anti-rotation function) Tightening torque: 1.2 N·m Gasket Locking Ring M22 P: 1 Panel Thickness 0.8 to 6		
Mou	nting Hole Plug	Polyamide	LW9Z-BP1	LW9Z-BP1	1	Degree of protection: IP65 Tightening torque: 2.0 N·m Q29.0 Q38et Locking Ring M22 P·1		
Swit	ch Guard Spring Return	Guard: Polyacetal Cover: polyarylate	HW9Z-K1	HW9Z-K1	1	Used to prevent inadvertent operation for flush pushbuttons. Degree of protection: IP65 Maintained type stops at 90° and 180°. 31 min.		
	Maintain	Gasket:	HW9Z-K11	HW9Z-K11	1	2 1 2 1 2 1 2 1 2 1 2 1 2 1 2 1 2 1 2 1		
Butt	on Clear Boot For flush pushbutto	Rubber (EPDM)	0C-31	00-31	1	Used to cover and protect pushbuttons where units are subject to watersplash. Not suitable for outdoor use or where the units are		
	For extended pushbutto		0C-32	0C-32	1	subject to oil splash. • Cannot be used with nameplates HWAM, HWAQ, HWAS, or HWAV.		

Accessories All dimensions in mm

when ordering, specify the ordering t						
Name / Shape	Material	Part No.	Ordering No.	Package Quantity	Remarks	
Padlock Cover	Polyarylate Gasket: Nitrile rubber	HW9Z-KL1	HW9Z-KL1	1	Used to protect pushbuttons, selector switches, and key selector switches. 82.5 Panel Thickness 0.8 to 3.2 Waterproof Rubber Gasket 0.5t 30	
Rubber Boot for Dual Pushbutton Switches	Clear Silicon Rubber	HW9Z-D7D	HW9Z-D7D	1	• IP65	
Ring Adapter	Nitryl rubber	HW9Z-A25	HW9Z-A25PN05	5	Used to install the HW series units into ø25 mm mounting holes. Degree of protection: IP65 Cannot be used with anti-rotation and nameplate. Mounting panel thickness: 1.2 to 6.0 mm See page 62 for details.	
Ring Adapter	Gasket: polyamide Washer: metal (brass)	HW9Z-A30	HW9Z-A30PN02	2	Used to install the HW series units (round type) into ø30 mm mounting holes (except HW1P-5, HW1E, HW1B-M5/V5, HW7D). Degree of protection: IP65 Cannot be used with anti-rotation ring and nameplate. Cannot be used on full shroud illuminated pushbuttons, selector pushbuttons, and mono-lever switches. Mounting panel thickness: 1.6 to 4.0 mm	
For Illuminated Buzzer Terminal Rubber Boot	Nitrile rubber	HW9Z-CZ1	HW9Z-CZ1	1	 Applicable cable: ø4.5 to 8.5 mm Cut the end of rubber boot to fit the cable size (see dimensions on page 66). Weight: 10 g (approx.) 	

Accessories All dimensions in mm

Name / Shape	Material	Part No.	Ordering No.	Package Quantity	Remarks			
Contact Block	NO contact Housing color: blue	HW-P10	HW-P10	5	Terminal no.: 1st deck 3-4			
	NC contact Housing color: reddish purple	HW-P01	HW-P01	5	Terminal no.: 1st deck: 1-2	Note) Switches with 1		
	2NO contact Housing color: blue	HW-PW20	HW-PW20	5	Terminal no.: 1 deck: 13-14 2 deck: 23-24	contact block contain 2 dummy blocks. Switches with 2 contact blocks contain 1 dummy block.		
-	2NC contact Housing color: reddish purple	HW-PW02	HW-PW02	5	Terminal no.: 1 deck: 11-12 2 deck: 21-22	i dullilly block.		
	NONC contact Housing color: blue / reddish purple	HW-PW11	HW-PW11	5	Terminal no.: 1 deck: 13-14 2 deck: 21-22			
Full voltage adapter								
		HW-CNP	HW-CNP	1	Connecting unit for Push-in terminal			
Connecting unit								
0	Weight: approx. 9g	HW-CNP	HW-CNP	1	Connecting unit for Push-in terminal			
Dummy Block	Polyamide (black)	CW-DB	CW-DBPN05	5	Note) Switches with 1 contact block contain 2 dummy blocks. Switches with 2 contact blocks contain 1 dummy block.			

Maintenance Parts

All dimensions in mm

	Name	/ Shape	Material/Dimensions	Part No.	Ordering No.	Package Quantity	Color Code *
Lens	2	①Round flush	Polyarylate ø23.5 H4.2	HW9Z-L11*	HW9Z-L11*-KPN05	5	R (red), G (green), Y (yellow), A (amber), C (clear), S (blue)
		©Square flush	Polyarylate ø24.6 H4	HW9Z-L21*	HW9Z-L21*-KPN05	5	
	3	③Round extended	Polyarylate ø23.3 H10	HW9Z-L12*	HW9Z-L12*-KPN05	5	
	(S)	€ø29 mushroom	AS, marking type ø29 H12.7	ALW31LD-*	ALW31LD-*-KPN02	2	
-		⑤ø40 mushroom	AS, marking type ø40 H12.7	ALW41LD-*	ALW41LD-*-K	1	
6		®Dome for pilot light	AS ø23.5 H15.1	HW1A-P2*	HW1A-P2*PN05-K	5	R (red), G (green), Y (yellow), A (amber), W (white), S (blue)
Butto		①Round flush with round or square bezel	Polyacetal ø23.6 H3	HW1A-B1*	HW1A-B1*PN05	5	Use ① for Selector pushbuttons
		②Round extended with round or square bezel	Polyacetal ø23.6 H9.2	HW1A-B2*	HW1A-B2*PN05	5	B (black), G (green), R (red),
3	4	③Square flush	Polyacetal □24.8 H3	HW2A-B1*	HW2A-B1*PN05	5	Y (yellow), S (blue), W (white)
(5		Square extended	Polyacetal □24.5 H9.2	HW2A-B2*	HW2A-B2*PN05	5	
	6	⑤ø29 mushroom	Polyacetal ø29 H12.7 (M18P1.0)	HW1A-B3*	HW1A-B3*PN02	2	
		©ø40 mushroom	Polyacetal ø40 H12.7 (M18P1.0)	HW1A-B4*	HW1A-B4*PN02	2	
	Round flush		Acrylic ø21.5 Thickness = 1	HW9Z-P11	HW9Z-P11PN05	5	White See page 63 for dimensions and engraving area.
Marking Plate	Round extended		Acrylic ø21.3 Thickness = 6.5	HW9Z-P12	HW9Z-P12PN05	5	
g Plate	Square flush		Acrylic 22.7 Thickness = 1	HW9Z-P21	HW9Z-P21PN05	5	
	ø29/40 mm mushroom		Acrylic ø15.7 H3.4	ALW3B	ALW3BPN05	5	
Operator Knob for Illuminated Selector Switch				HW9Z-FDY*	HW9Z-FDY*-K	1	R (red), G (green), Y (yellow), A (amber), W (white), S (blue)
Opera	tor Lever for Illumi	nated Selector Switch	AS resin	HW9Z-FDL*	HW9Z-FDL*-K	1	
			Metal (nickel-plated brass)	HW9Z-SK-231	HW9Z-SK-231PN02	2	

Maintenance Parts All dimensions in mm

When ordering, specify the Ordering No.

Name / Shap	е	Material/Dimensions	Part No.	Ordering No.	Package Quantity	Remarks
Spare Key (Pin Tumber Key)		Metal	LW9Z-SK-500	LW9Z-SK-500PN02	_	Standard key number
e de		(nickel-plated brass)	LW9Z-SK-	LW9Z-SKPN02	2	• Key number: 501 to 515
Lockig Ring		Polyamide (black) ø28.4 H5 M22P1	HW9Z-LN	HW9Z-LNPN05	5	
Cap for Mono-lever Switch	Standard	Nitryl rubber ø10 L20	HW9Z-CPM	HW9Z-CPM	1	
Boot for Mono-lever Switch	Standard	Nitryl rubber ø29.2 L34.4	HW9Z-BLM	HW9Z-BLM	1	
Gasket		Nitryl rubber (black)	HW9Z-WM	HW9Z-WMPN10	10	Thickness = 0.5 0.15 0.15 0.28.0 2.0.15

HW Series LED Lamps

NW Series LED Lamps Current Draw			nt Draw			When ordering, specify the Orde	
Shape/Dimensions	Operating Voltage	DC	AC	Part No.	Ordering No.	Package Quantity	Base
	6V AC/DC 10mA	10mA	14mA	LSRD-6	LSRD-6	1	
C	OV AC/DC	TOTIA	14IIIA	LOND-0	LSRD-6PN10	10	
	12V AC/DC	7mA	8mA	LSRD-1	LSRD-1	1	
(20.5)	124 A0/00	7 IIIA	OIIIA	OHA LOND-1	LSRD-1PN10	10	BA9S/13
2.4 (20.5)	24V AC/DC	7mA 8mA	8m∆	BmA LSRD-2	LSRD-2	1	
Voltage No.	211710750	71101	OH#Y		LSRD-2PN10	10	
\text{\voltage}{Base (X2)} \text{Eyelet (X1)}	100/120V	2mA 2mA	LSRD-H2	LSRD-H2	1		
	AC/DC				LSRD-H2PN10	10	
	200/220V AC	2mA	2mA 2mA LSRD-M2	nΔ I SRD-M2	LSRD-M2	1	
				LSRD-M2PN10	10		
	230/240V AC	2mA 2mA	2mA	LSRD-M4	LSRD-M4	1	
				J	LSRD-M4PN10	10	

Maintenance Parts All dimensions in mm.

When ordering, specify the Ordering No.


Shape	Operating Voltage	Operating Voltage Range	Ordering No.	Applicable Load
6V	400/440V AC	400/440V AC ±10%	TWR546	LSRD-6 (6V AC/DC, LED lamp)
24V	400/440V AC	400/440V AC ±10%	TWR542	LSRD-2 (24V AC/DC, LED lamp)

- Terminal cover (TWR-VL3) is installed on transformers as standard.
- Transformer is installed to one HW series unit.

Specifications

Part No.	TWR5□6	TWR5□2	
Operating Voltage	400/440V AC (50/60Hz)		
Current Draw	2.4VA		
Rated Insulation Voltage	600V		
Insulation Resistance	100MΩ minimum (500V [OC megger)	
Operating Temperature	-30 to +60°C (no freezing	g)	
Operating Humidity	35 to 85% RH (no condensation)		
Storage Temperature	-40 to +80°C (no freezing)		
Vibration Resistance	Damage limits: 30Hz, amplitude 1.5 mm Operating extremes: 5 to 55Hz, amplitude 0.5 mm		
Shock Resistance	Damage limits: 1,000 m/s ² Operating extremes: 100 m/s ²		
Dielectric Strength	2500V AC, 1 minute		
Terminal Screw	M3.5		
Applicable Wire	2mm² maximum, 2 wires maximum		
Weight (approx.)	87g		

Dimensions



All dimensions in mm.

Accessories

When ordering, specify the Ordering No.

Shape	Material	Part No.	Ordering No.	Package Quantity	Dimensions (mm)
DIN 35 mm Rail Weight: 200g approx.	Aluminum Length: 1000 mm	BAA1000	BAA1000PN10	10	12.5
End Clip Weight: 15g approx.	Metal (zinc-plated steel) Applicable rail: BAA1000 BAP1000	BNL6	BNL6PN10	10	M4 Screws

\triangle


Safety Precautions

- Turn off the power to the HW series switches & pilot lights before starting installation, removal, wiring, maintenance, and inspection of the products. Failure to turn power off may cause electrical shocks or fire hazard.
- To avoid a burn on your hand, use the lamp holder tool when replacing lamps.
- For wiring, use wires of a proper size to meet the voltage, current requirements, and the number of connectable wires (page 65). Failure to tighten the terminal screws may cause overheating and fire.
- Avoid using in places mentioned below to maintain performance of the product.
 - -Exposed to direct sunlight
- -Subject to corrosive or flammable gases

Instructions

Panel Mounting

- 1. Remove the contact block from the operator.
- 2. Remove the locking ring from the operator
- Insert the operator into the panel cut-out from the front. When mounting the nameplate, insert between the operator and panel.
- 4. Tighten the locking ring from the back.



Mounting panel thickness is reduced by 1.5 mm when using a nameplate.

Removing the Contact Block


- Remove the operator from the contact block by pushing and turning the locking lever in the direction of the arrow shown below. Then the operator can be pulled out.
- To reinstall, place the TOP marking on the operator and the lock lever in the same direction, and insert the operator into the contact block mounting adapter. Then turn the locking lever in the opposite direction.





Anti-rotation Ring and Mounting Panel

Turn the TOP marking on the operator and the \triangle mark on the antirotation ring to the recess on the mounting panel.



Installing the Pilot Light

Detach the operator unit from the LED unit. After mounting the operator from the front of the panel, attach the LED unit.

Installing / Removing the LED Unit

1. Detach the LED unit by lifting the latch using a small flat blade screwdriver width 0.5mm max.



To install, align the TOP marking on the operator with the TOP marking on the LED unit.



Notes for Panel Mounting

Locking ring wrench recommended torque
Tighten the bezel to a tightening torque of 2.0 N·m.

Locking ring wrench (MW9Z-T1) can be used to tighten the bezel. Do not use pliers. Excessive tightening will damage the locking ring.



Locking ring wrench (MW9Z-T1)

Panel Thickness

HW series can be mounted on a panel with thickness of 0.8 to 6.0 mm (switches) and 0.8 to 4.5 mm (pilot lights). Take the thickness of nameplate and/or switch guard into consideration.

Replacing LED Lamps

Lamps can be replaced using the lamp holder tool (OR-55) from the front of the panel, or by removing the contact block from the operator unit. (See page 53 for lamp holder tool.)

Removing the LED lamp from the front of the panel Removing

To remove, slip the lamp holder tool onto the lamp head lightly. Then push slightly, and turn the lamp holder tool counterclockwise.



Installing

Insert the lamp head into the lamp holder tool.



Place the pins on the lamp base to the grooves in the lamp socket. Insert the lamp and turn it clockwise.

Removing and Installing the Contact Blocks, Dummy Blocks, and LED Units

Removing


To remove the contact block and dummy block, insert into the flat blade screwdriver latch and move in the direction of the arrow.



Installing

When installing the contact block or dummy block, make sure that it snaps on to the operator.

For No. 1 and 3 only a contact block or dummy block can be installed. For No. 2, only a dummy block can be installed.




Note) Make sure to attach a correctly assembled connection unit to the operator.

Note) When attaching the contact block to the connection unit, make sure that the connection is detached from the operator. If a contact block is installed with the operator attached to the connection unit, malfunction of the switch may occur.

Note) Full voltage adapters cannot be removed or atached with contact blocks attached.

Note) Attach the full voltage adapter vertically to the connection unit.



Test Points

Note) Do not insert wires into the test point.

Single contact block


Note) When conducting a continuity test on the contact block, make sure that probes (ø2.0 maximum) of the tester are inserted vertically to the panel.



Double contact block

When conducting a continuity test on the first deck, make sure that probes $(\emptyset 2.0 \text{ maximum})$ of the tester are inserted in an angle of the contact block, in two places as shown below.

When conducting a continuity test on the second deck, make sure that probes (ø2.0 maximum) of the tester are inserted vertically to the panel.



Installing/Removing the Lenses and Marking Plates

Insert a flat screwdriver in groove of the lens (TOP mark side of the

operator or opposite side) to remove the lens unit (lens/marking plate/

Instructions

Installing/Removing the Buttons and Lenses

<To install>

<To remove>

Pushbutton Button

Flush/Extended

Push in the button to install.



Insert a flat screwdriver between the button and the bezel to remove the button.



• Mushroom/Jumbo Mushroom

Button has threads. Turn clockwise to install the button.



Turn the button counterclockwise to remove.

Note: Jumbo mushroom button cannot be removed.



Removing the lens

Removing

lens holder).

Removing the lens unit

Remove the lens by pushing the lens from the rear to disengage the latches between the lens and the lens holder, using a flat screwdriver




The translucent filter in the lens holder cannot be removed because this filter is sealed to make the unit waterproof and oiltight.

Installing

- 1. Place the marking plate on the lens holder with the anti-rotation projection engaged and press the lens onto the lens holder to engage the latches.
- 2. Place the marking plate in the correct orientation.

For Square Lens (square flush lens)



Illuminated Pushbutton Lens

Flush/Extended

Push in the lens holder into the operator unit.



Insert a flat screwdriver between the button and the bezel to remove the lens holder.



• Mushroom/Jumbo Mushroom

Lens has threads. Turn clockwise to install the lens.



Lens has threads. Turn counterclockwise to remove the lens.



Pilot Light Lens

Extended

Lens has threads. Turn clockwise to install the lens.



Turn the lens counterclockwise to remove.



Square Flush

Push in the lens holder into the operator unit.




Insert a flat screwdriver between the lens and the bezel to remove.



Using a Ring Adapter


HW9Z-A25

Install the ring adapter between the HW series unit and panel. Make sure that the side with ridges face the panel.




HW9Z-A30

The ring adapter HW9Z-A30 consists of a washer and adapter. Install adapter between the HW series unit and panel. Install washer between the locking ring and panel.



Dual Pushbutton Switches

The pushbuttons cannot be removed or replaced. Do not attempt to remove using a flat screwdriver or pincers, otherwise the pushbuttons may be damaged.




Installing the Rubber Boot for Dual Pushbuttons


When using the HW7D pushbuttons in places where the pushbuttons are subject to water splash or an excessive amount of dust, make sure to use the HW9Z-D7D rubber boot (IP65) which is ordered separately. Remove the rubber gasket pre-installed on the operator, and install the rubber boot from the front of the button.

Notes for Installing the Rubber Boot

Remove the gasket from the operator, and install the rubber boot on the operator. Pull out the seals of the rubber boot and place them around the operator sleeve as shown. Make sure that the seals are not twisted or tucked inside and that the gasket does not remain, otherwise the normal waterproof and dustproof characteristics are not ensured.



Rubber Boot Installed



Selector Switches

Turn the operator such as knob, lever, and key to each position accurately. Releasing halfway may cause the operator to return to the former position, or to get stuck between. On spring return two-way types, the center of operators may be misaligned slightly.

Key Selector Switches


Observe the following instructions to prevent malfunction or damage.

- Turn the key securely to each position.
- Insert the key to the bottom of the key hole.
- Do not remove the key from any key retained position.
- Use a key that matches with the number on the key cylinder.
 However, for standard keys, the key number is engraved on the key but not on the key cylinder.

Marking

For HW series pilot lights, legends and symbols can be engraved on the built-in marking plates, or printed film can be inserted under the lens for labeling purposes.


Marking plate and marking film size (mm)



^{*}Marking films are not supplied.

Insertion Order of Marking Plate and Film

Square Lens (Square flush lens)



Note: Films are not supplied. When inserting a film, make sure that the marking plate is installed with its uneven side facing the lens holder.

Nameplate


Mounting panel thickness is reduced by 1.5 mm when using a nameplate. $$_{\mbox{\scriptsize Nameplate}}$$

Installing a Marking Plate

Insert a marking plate tin the direction of the arrow $\ensuremath{\mathfrak{D}},$ and press in as shown $\ensuremath{\mathfrak{D}}.$



Insert a flat screwdriver into the upper middle part of the marking plate and remove. When anti-rotation is not required, remove the projection from the nameplate using pliers.




Applicable Wire

When wiring, use the applicable wires shown below.

Applicable Wire and Specifications

Applicable Wire (*1)	0.25 to 1.5mm ² (AWG16 to 24)
Wire Strip Length (*2)	8 ± 1mm (*3)
Ferrule Size (*3)	H0.25 to H1.5 (without insulated cover)
(Weidmüller)	H0.25 to H1.5 (with insulated cover)

- *1) For applicable wires confirmed by IDEC, see website.
- *2) For details on ferrules, see "Wire Size and Recommended Ferrules" table below.
- *3) Strip the sheath of the wire 8±1mm from the end.



lote: Make sure that the stranded wires do not loosen when using wiring without ferrules

Wire Size and Recommended Ferrules

Ferrules without insulated covers

Applicable Wire (Stranded Wire) AWG mm²		Wire Strip Length	Weidmüller Recommended Part No.
24	0.25	5 to 6mm	H0.25/5
20	0.50	10 to 11mm	H0.5/10
18	0.75	10 to 11mm	H0.75/10
18	1.00	10 to 11mm	H1.0/10
16	1.50	10 to 11mm	H1.5/10

Ferrules with insulated covers


Citatos With insulator covers				
	ble Wire ed Wire)	Wire Strip Length	Weidmüller Recommended Part No.	
AWG	mm²	Lengui		
24	0.25	10 to 11mm	H0.25/12 HBL	
22	0.34	10 to 11mm	H0.34/12 TK	
20	0.50	10 to 11mm	H0.5/14 OR	
18	0.75	10 to 11mm	H0.75/14 W	
18	1.00	10 to 11mm	H1.0/14 GE	
16	1.50	10 to 11mm	H1.5/14 R	

Recommended Tools (Optional)

Name	Weidmüller Recommended Part No.
Crimping tool	PZ 6 ROTO L
Flat blade screwdriver	SDS 0.4×2.0×60
FIAL DIAUE SCIEWUITVEI	SDS 0.4×2.5×75

Note 1) Note the crimping dimensions When using tools other than the recommended crimping tool. For details, see page 65.

Note 2) Use a flat blade screwdriver with a blade size of 0.4×2 to 2.5 mm.




• For details on crimping tools, see page 55.

Wiring Procedure

Connecting the wire


Stranded wires with ferrules or solid wire

- ① Insert the wire to the back of the wire port.
- ② After wiring, tug lightly to make sure that the wire is properly connected.




Stranded wire

- ① While pressing the pusher (orange button) using a flat blade screwdriver (recommended: SDS 0.4×2.0×60 (optional). Insert the wire fully in the wiring port. Wire is connected when the pusher is released.
- ② After wiring, tug lightly to make sure that the wire is properly connected.



Crimping of Ferrules and Wiring


- Choose an appropriate ferrule for the wire.
- Cut the wire carefully to get a flat end.
- Make sure that ferrule sleeve is completely filled by the conductor.
 Depending on the cross section, the conductor should protrude approx. 0 to 1 mm from the ferrule sleeve.



• When crimping, refer to the instructions of the crimping tool.

Faults which can occur during crimping:

- Cracks along the sides and die impressions
- Splitting of the ferrules
- · Asymmetrical crimping shape
- Extreme burrs formed along the sides
- · Ferrule not filled by conductor
- · Single conductors pushed back by protruding from the insulated cover
- Single conductors squeezed off
- Insulation cover damaged by the crimping jaw
- Conductor insulation not pushed into the insulated cover
- Ferrule bent longitudinally after crimping



Formation of cracks at the sides. Sides spilt open

Formation of cracks at the impressions of the crimping jaw

Asymmetrical crimping shape. Burr formation on one side



Asymmetrical crimping shape. Burr formation on one side


Single conductor squeezed off



Single conductor pushed back

Crimping dimensions: W2.4×H1.9 mm

Maximum connectable crimping size is W2.4 \times H1.9. Make sure that the ferrule size will be smaller than this dimension. (Recommended crimping tool: PZ 6 Roto (optional) Weidmüller




Note 1) If a tool other than the recommended crimping tool is used, the ferrule may not be crimped to the appropriate size and the clamp or spring inside the contact block may be deformed and may not operate normally.

Note 2) Pin crimp terminals cannot be used.

Removing the Wire

When removing the wire, push the pusher using a flat blade screwdriver (recommended: SDS $0.4\times2.0\times60$ (optional: see page 55)) and pull wire out in the direction of the arrow.



<Notes>

- Operate the pusher with a force of 20N. Do not press excessively. Otherwise, the switch may be damaged.
- Do not pull the wire out without depressing the pusher. When pulling the wire, be sure to pull in a straight direction. Otherwise, the socket may be damaged.

Number of Connectable Wires

Unit	Connectable wires		No. of connectable wires
	Solid wire	0.25 to 1.5mm ² (AWG16 to 24)	
HW-P	Stranded wire 0.25 to 1.5mm ² (AWG16 to 24)		
Contact block Pilot light	Ferrule	Without insulated cover 0.25mm²: conductor length:5 to 10mm 0.5 to 1.0mm²: conductor length: 6 to 10mm 1.5mm²: conductor length 8 to 10mm With insulated cover 0.25 to 1.0mm²: conductor length 6 to 10mm 1.5mm²: conductor length 8 to 10mm Note) Pin terminals cannot be used	2

Note) Only one wire can be inserted into one wire port.

Instructions (Illuminated / Non-illuminated Buzzers)

Installing the terminal rubber boot

- 1. Cut the end of terminal rubber boot to fit the cable size.
- 2. Insert the cable into the terminal rubber boot in the direction of arrow shown below.

 Cut here when cable size is ø5.5 to 6.5 mm

 Cut here when cable size is ø6.5 to 7.5 mm

 Cut here when cable size is ø7.5 to 8.5 mm
- 3. Strip the insulation of the cable 30 mm from the end and wire as instructed in "Wiring".
- 4. Install the terminal rubber boot as shown below.



5. Cover part B with part A.




6. Make sure that the bellows is 17 to 22 mm long.



Note for terminal rubber boot

- Be sure to use bellows with an appropriate length. Otherwise, waterproof characteristics cannot be achieved.
- Maintain a cable angle of 45° maximum to the axis of the buzzer, otherwise the terminal rubber boot may come off.



Panel Mounting

• Insert the buzzer into the panel cut-out from the front, and tighten the locking ring from the back.

Note for panel mounting

- Use the optional locking ring wrench (MW9Z-T1) to tighten the locking ring to a recommended tightening torque of 1.5 to 2.0 N·m.
- Do not use pliers and do not tighten excessively, otherwise the buzzer may be damaged.



Wiring Procedure

Connecting the wire

Solid wire

Strip the insulation of the cable from 8mm from the end and insert into the wire port.

After wiring, tug lightly to make sure that the wire is properly connected.

Stranded wire with ferrule

Crimp a ferrule with a conductor length of 8mm and insert to the back of the wire port. After wiring, tug lightly to make sure that the wire is properly connected.

Recommended ferrule

Item	Phoenix Contact Recommended Part No.	Weidmüller Recommended Part No.
Ferrule	A0,5-8	
(without insulation	A0,75-8	_
cover)	A1-8	
	AI0,25-8YE	H0.25/12HBL
Ferrule (with insulation cover)	AI0,5-8WH	H0.5/140R
(COVEI)	AI0,75-8GY	H0.75/14W

Stranded wire

Strip the wire insulation 8mm from the end and push in the wire removal part above the wire port using a small flat screwdriver. Release the wire removal part. Make sure that the wire does not loosen.

Wire Removal Part



Wire removal

Push in the white wire removal part above the wire ports using a small flat screw driver, and pull out the wire.

Flat blade screwdriver

Use a optional flat blade screwdriver (SDS 0.4×2.5×75 (see page 42)) or a commercial screwdriver (blade shape: straight, blade size 2.5mm)

Notes for wiring

- Make sure that the terminal is not constantly pulled by the wire.
- Wiring must be performed in environments of -5 to +50°C.
- Do not damage the conductor wire when stripping the wire insulation.
- Do not use wires with bent or deformed conductors wires. Deformed wiring may cause failures such as strength degradation and overheating. Connect one wire per terminal. Connecting two wires to a terminal may cause loose wiring and strength degradation.
- Do not solder the conductor lines. Connecting soldered stranded wires may loose wiring and strength degradation.
- If a stranded wire has loose wires, twist the conductor wires before connection. However be careful not to twist excessively.

Instructions (Emergency Stop Switches)

When using the HW series control units in a safety-related circuit of a control system, observe safety rules and regulations of each country concerning particular applications of the actual machines and facilities. Perform risk assessment before operation to ensure safety.


Chattering / Contact Bounce

When the button is reset by pulling or turning, the NC main contacts will bounce. When pressing the button, the NO monitor contacts will bounce. When designing a control circuit, take the contact bounce time into consideration (reference value: 20 ms).

Also, do not apply shock to the switch as chattering may occur.

Nameplate or Switch Guard

When anti-rotation is not required, remove the projection from the nameplate or switch guard using pliers. Mechanical indicator types have projections on the operator. Make sure to remove the projection on the nameplate or switch guard.



Handling

Do not expose the switch to excessive shocks and vibrations, otherwise the switch may be deformed or damaged, causing malfunction or operation failure.



Ordering Terms and Conditions

Thank you for using IDEC Products.

By purchasing products listed in our catalogs, datasheets, and the like (hereinafter referred to as "Catalogs") you agree to be bound by these terms and conditions. Please read and agree to the terms and conditions before placing your order.

1. Notes on contents of Catalogs

- (1) Rated values, performance values, and specification values of IDEC products listed in this Catalog are values acquired under respective conditions in independent testing, and do not guarantee values gained in combined
 - Also, durability varies depending on the usage environment and usage conditions.
- (2) Reference data and reference values listed in Catalogs are for reference purposes only, and do not guarantee that the product will always operate appropriately in that range.
- (3) The specifications / appearance and accessories of IDEC products listed in Catalogs are subject to change or termination of sales without notice, for improvement or other reasons.
- (4) The content of Catalogs is subject to change without notice.

2. Note on applications

- (1) If using IDEC products in combination with other products, confirm the applicable laws / regulations and standards.
 - Also, confirm that IDEC products are compatible with your systems, machines, devices, and the like by using under the actual conditions. IDEC shall bear no liability whatsoever regarding the compatibility with IDEC products.
- (2) The usage examples and application examples listed in Catalogs are for reference purposes only. Therefore, when introducing a product, confirm the performance and safety of the instruments, devices, and the like before use. Furthermore, regarding these examples, IDEC does not grant license to use IDEC products to you, and IDEC offers no warranties regarding the ownership of intellectual property rights or non-infringement upon the intellectual property rights of third parties.
- (3) When using IDEC products, be cautious when implementing the following.
 - Use of IDEC products with sufficient allowance for rating and performance
 - Safety design, including redundant design and malfunction prevention design that prevents other danger and damage even in the event that an
 - iii. Wiring and installation that ensures the IDEC product used in your system, machine, device, or the like can perform and function according to its specifications
- (4) Continuing to use an IDEC product even after the performance has deteriorated can result in abnormal heat, smoke, fires, and the like due to insulation deterioration or the like. Perform periodic maintenance for IDEC products and the systems, machines, devices, and the like in which they are used.
- (5) IDEC products are developed and manufactured as general-purpose products for general industrial products. They are not intended for use in the following applications, and in the event that you use an IDEC product for these applications, unless otherwise agreed upon between you and IDEC, IDEC shall provide no guarantees whatsoever regarding IDEC products.
 - Use in applications that require a high degree of safety, including nuclear power control equipment, transportation equipment (railroads / airplanes / ships / vehicles / vehicle instruments, etc.), equipment for use in outer space, elevating equipment, medical instruments, safety devices, or any other equipment, instruments, or the like that could endanger life or human health
 - Use in applications that require a high degree of reliability, such as provision systems for gas / waterworks / electricity, etc., systems that operate continuously for 24 hours, and settlement systems
 - Use in applications where the product may be handled or used deviating from the specifications or conditions / environment listed in the Catalogs, such as equipment used outdoors or applications in environments subject to chemical pollution or electromagnetic interference If you would like to use IDEC products in the above applications, be sure to consult with an IDEC sales representative.

3. Inspections

We ask that you implement inspections for IDEC products you purchase without delay, as well as thoroughly keep in mind management/maintenance regarding handling of the product before and during the inspection.

4. Warranty

(1) Warranty period

The warranty period for IDEC products shall be one (1) year after purchase or delivery to the specified location. However, this shall not apply in cases where there is a different specification in the Catalogs or there is another agreement in place between you and IDEC.

(2) Warranty scope

Should a failure occur in an IDEC product during the above warranty period for reasons attributable to IDEC, then IDEC shall replace or repair that product, free of charge, at the purchase location / delivery location of the product, or an IDEC service base. However, failures caused by the following reasons shall be deemed outside the scope of this warranty.

- The product was handled or used deviating from the conditions / environment listed in the Catalogs
- The failure was caused by reasons other than an IDEC product
- Modification or repair was performed by a party other than IDEC
- The failure was caused by a software program of a party other than IDEC
- The product was used outside of its original purpose
- Replacement of maintenance parts, installation of accessories, or the like was not performed properly in accordance with the user's manual and
- vii. The failure could not have been predicted with the scientific and technical standards at the time when the product was shipped from IDEC.
- The failure was due to other causes not attributable to IDEC (including cases of force majeure such as natural disasters and other disasters)

Furthermore, the warranty described here refers to a warranty on the IDEC product as a unit, and damages induced by the failure of an IDEC product are excluded from this warranty.

5. Limitation of liability

The warranty listed in this Agreement is the full and complete warranty for IDEC products, and IDEC shall bear no liability whatsoever regarding special damages, indirect damages, incidental damages, or passive damages that occurred due to an IDEC product.

6. Service scope

The prices of IDEC products do not include the cost of services, such as dispatching technicians. Therefore, separate fees are required in the following cases.

- (1) Instructions for installation / adjustment and accompaniment at test operation (including creating application software and testing operation, etc.)
- (2) Maintenance inspections, adjustments, and repairs
- (3) Technical instructions and technical training
- (4) Product tests or inspections specified by you

The above content assumes transactions and usage within your region. Please consult with an IDEC sales representative regarding transactions and usage outside of your region. Also, IDEC provides no guarantees whatsoever regarding IDEC products sold outside your region.

DEC CORPORATION

Head Office

6-64, Nishi-Miyahara-2-Chome, Yodogawa-ku, Osaka 532-0004, Japan

IDEC Corporation Tel: +1-408-747-0550 opencontact@idec.com Germany APEM GmbH Tel: +49-40-25 30 54-0 service@eu.idec.com Singapore IDEC Izumi Asia Pte. Ltd. Tel: +65-6746-1155 info@sa.idec.com Thailand IDEC Asia (Thailand) Co., Ltd Tel: +66-2-392-9765 sales@th.idec.com Australia IDEC Australia Pty. Ltd. Tel: +61-3-8523-5900 sales@au.idec.com IDEC Controls India Private Limited Tel: +91-80679-35328 info_india@idec.com

Hong Kong China

Beijing Branch Guangzhou Branch **IDEC Corporation**

IDEC Taiwan Corporation IDEC Izumi (H.K.) Co., Ltd. IDEC (Shanghai) Corporation

Tel: +886-2-2577-6938 Tel: +852-2803-8989 Tel: +86-21-6135-1515

→ www.idec.com

service@tw.idec.com info@hk.idec.com idec@cn.idec.com Tel: +86-10-6581-6131 idec@cn.idec.com Tel: +86-20-8362-2394 idec@cn.idec.com Tel: +81-6-6398-2527 marketing@idec.co.jp

