



### SPECIFICATIONS

**CUSTOMER** : POWERTIP  
**SAMPLE CODE (Ver.)** : \_\_\_\_\_  
(This Code will be changed while mass production)  
**MASS PRODUCTION CODE (Ver.)** : PC1602LRS-LWA-H-YM (Ver.0)

**Customer Approved**

**Date:** \_\_\_\_\_

| Sales Sign | QC Confirmed | Checked  | Designer  |
|------------|--------------|--|---|
|            |              | <br>Leo Ki-Din | <br>黃其仁/2004 |

- Approval For Specifications Only.  
 \* This specification is subject to change without notice.  
 Please contact Powertip or it's representative before designing your product based on this specification.
- Approval For Specifications and Sample.

### Powertip Corporation

**Headquarters:**

|   |                      |  |
|---|----------------------|--|
| No.6, 6 <sup>th</sup> Road, Taichung Industrial Park, | TEL: 886-4-2355-8168 | E-mail: <a href="mailto:sales@powertip.com.tw">sales@powertip.com.tw</a> |
| Taichung, Taiwan                                      | FAX: 886-4-2355-8166 | Http:// <a href="http://www.powertip.com.tw">www.powertip.com.tw</a>     |
| 台中市 407 工業區六路 8 號                                     |                      |  |



## ***Contents***

### **1. SPECIFICATIONS**

- 1.1 Features**
- 1.2 Mechanical Specifications**
- 1.3 Absolute Maximum Ratings**
- 1.4 DC Electrical Characteristics**
- 1.5 Optical Characteristics**
- 1.6 Backlight Characteristics**

### **2. MODULE STRUCTURE**

- 2.1 Counter Drawing**
- 2.2 Interface Pin Description**
- 2.3 Timing Characteristics**
- 2.4 Display Command**
- 2.5 Character Pattern**

### **3. QUALITY ASSURANCE SYSTEM**

- 3.1 Quality Assurance Flow Chart**
- 3.2 Inspection Specification**

### **4. RELIABILITY TEST**

- 4.1 Reliability Test Condition**

### **5. PRECAUTION RELATING PRODUCT HANDLING**

- 5.1 Safety**
- 5.2 Handling**
- 5.3 Storage**
- 5.4 Terms of Warranty**

**Note :** For detailed information please refer to IC data sheet : [ST7066U,KS0065B](#)

## 1. SPECIFICATIONS

### 1.1 Features

| Item              | Standard Value                                     |
|-------------------|--|
| Display Type      | 16 * 2 characters                                  |
| LCD Type          | STN, Gray, Transflective, Positive, Extended Temp. |
| Driver Condition  | LCD Module : 1/16 Duty , 1/5 Bias                  |
| Viewing Direction | 6 O'clock  |
| Backlight         | YG LED B/L   |
| Weight            | 67 g   |
| Interface         | —  |
| Other             | —  |

### 1.2 Mechanical Specifications

| Item              | Standard Value                    | Unit |
|-------------------|-----------------------------------|------|
| Outline Dimension | 122.0(L) * 44.0(w) * 14.0(H)(Max) | mm   |
| Viewing Area      | 99.0(L) * 24.0(w)                 | mm   |
| Active Area       | 94.84(L) * 20.0(w)                | mm   |
| Dot Size          | 0.92(L) * 1.10(w)                 | mm   |
| Dot Pitch         | 0.98(L) * 1.16(w)                 | mm   |

Note : For detailed information please refer to LCM drawing

### 1.3 Absolute Maximum Ratings

| Item                      | Symbol           | Condition    | Min.                  | Max.                 | Unit |
|---------------------------|------------------|--------------|-----------------------|----------------------|------|
| Power Supply Voltage      | V <sub>DD</sub>  | —            | -0.3                  | 7.0                  | V    |
| LCD Driver Supply Voltage | V <sub>LCD</sub> | —            | V <sub>DD</sub> -10.0 | V <sub>DD</sub> +0.3 | V    |
| Input Voltage             | V <sub>IN</sub>  | —            | -0.3                  | V <sub>DD</sub> +0.3 | V    |
| Operating Temperature     | T <sub>OP</sub>  | Excluded B/L | -20                   | 70                   | °C   |
| Storage Temperature       | T <sub>ST</sub>  | Excluded B/L | -30                   | 80                   | °C   |
| Storage Humidity          | H <sub>D</sub>   | Ta < 40 °C   | -                     | 90                   | %RH  |

### 1.4 DC Electrical Characteristics

$V_{DD} = 5.0 \pm 0.2V$  ,  $V_{SS} = 0V$  ,  $T_a = 25^\circ C$


| Item                 | Symbol   | Condition                     | Min.         | Typ.  | Max.     | Unit |
|----------------------|----------|-------------------------------|--------------|-------|----------|------|
| Logic Supply Voltage | $V_{DD}$ | —                             | 4.8          | 5.0   | 5.2      | V    |
| “H” Input Voltage    | $V_{IH}$ | —                             | $0.7 V_{DD}$ | -     | $V_{DD}$ | V    |
| “L” Input Voltage    | $V_{IL}$ | —                             | -0.3         | -     | 0.6      | V    |
| “H” Output Voltage   | $V_{OH}$ | $I_{OH} = -0.1mA$             | 3.9          | -     | $V_{DD}$ | V    |
| “L” Output Voltage   | $V_{OL}$ | $I_{OL} = 0.1mA$              | -            | -     | 0.4      | V    |
| Supply Current       | $I_{DD}$ | $V_{DD} = 5.0 V$              | -            | 1.3   | -        | mA   |
| LCM Driver Voltage   | $V_{OP}$ |                               |              |       |          | V    |
|                      |          | $-20^\circ C \sim 70^\circ C$ |              | Fixed |          |      |
|                      |          |                               |              |       |          |      |

### 1.5 Optical Characteristics

LCD Panel : 1/16 Duty , 1/4 Bias ,  $V_{LCD} = 4.2 V$  ,  $T_a = 25^\circ C$


| Item                | Symbol   | Conditions                                | Min.       | Typ.   | Max.    | Reference   |
|---------------------|----------|---|------------|--------|---------|-------------|
| View Angle          | $\theta$ | $C \geq 2.0, \varnothing = 0^\circ$       | $40^\circ$ | -      | -       | Notes 1 & 2 |
| Contrast Ratio      | C        | $\theta = 5^\circ, \varnothing = 0^\circ$ | 3          | 5      | -       | Note 3      |
| Response Time(rise) | $t_r$    | $\theta = 5^\circ, \varnothing = 0^\circ$ | -          | 80 ms  | 120ms   | Note 4      |
| Response Time(fall) | $t_f$    | $\theta = 5^\circ, \varnothing = 0^\circ$ | -          | 170 ms | 262.5ms | Note 4      |

Note 1: Definition of angles  $\theta$  and  $\varnothing$



Light (when reflected)  $z(\theta=0^\circ)$   
 $Y(\varnothing=180^\circ)$   
 $X(\varnothing=90^\circ)$   
 Light (when transmitted)  $Y(\varnothing=0^\circ)$   
 $(\theta=90^\circ)$


Note 2: Definition of viewing angles  $\theta_1$  and  $\theta_2$




Note : Optimum viewing angle with the naked eye and viewing angle  $\theta$  at  $C_{max}$ . Above are not always the same

Note 3: Definition of contrast C

$$C = \frac{\text{Brightness (reflection) of unselected dot (B2)}}{\text{Brightness (reflection) of selected dot (B1)}}$$



Note 4: Definition of response time



Note: Measured with a transmissive LCD panel which is displayed 1 cm<sup>2</sup>

$V_{LCD}$  : Operating voltage  $f_{FRM}$  : Frame frequency  
 $t_r$  : Response time (rise)  $t_f$  : Response time (fall)

## 1.6 Backlight Characteristics

LCD Module with LED Backlight


### Maximum Ratings

| Item                      | Symbol          | Conditions | Min. | Max. | Unit |
|---------------------------|-----------------|------------|------|------|------|
| Forward Current           | IF              | Ta =25°C   | -    | 480  | mA   |
| Reverse Voltage           | VR              | Ta =25°C   | -    | 8    | V    |
| Power Dissipation         | PO              | Ta =25°C   | -    | 2.2  | W    |
| Operating Temperature     | T <sub>OP</sub> | -          | -20  | 70   | °C   |
| Storage Temperature       | T <sub>ST</sub> | -          | -40  | 90   | °C   |
| Solder Temp. for 3 Second | -               | -          | -    | 260  | °C   |

### Electrical / Optical Characteristics

Ta =25°C

| Item                                | Symbol       | Conditions | Min. | Typ. | Max. | Unit              |
|-------------------------------------|--------------|------------|------|------|------|-------------------|
| Forward Voltage                     | VF           | IF=240mA   | 4.0  | 4.2  | 4.6  | V                 |
| Wavelength                          | λ p          | IF=240mA   | -    | 570  | 572  | nm                |
| Luminous Intensity<br>(without LCD) | IV           | IF=240mA   | 80   | 100  | -    | cd/m <sup>2</sup> |
| Color                               | Yellow-green |            |      |      |      |                   |






## 2.2 Interface Pin Description


| Pin No. | Symbol           | Signal Description  |
|---------|------------------|---|
| 1       | VSS              | Power Supply ( $V_{SS}=0$ )   |
| 2       | VDD              | Power Supply ( $V_{DD}>V_{SS}$ )  |
| 3       | VO               | NC.   |
| 4       | RS               | Register Selection input<br>High = Data register<br>Low = Instruction register (for write)<br>Busy flag address counter (for read)                                  |
| 5       | $\overline{R/W}$ | Read/Write signal input is used to select the read/write mode<br>High = Read mode, Low = Write mode   |
| 6       | E                | Start enable signal to read or write the data   |
| 7~10    | DB0 ~ DB3        | Four low order bi-directional three-state data bus lines. Use for data transfer between the MPU and the LCD module. These four are not used during 4-bit operation. |
| 11~14   | DB4 ~ DB7        | Four high order bi-directional three-state data bus lines. Used for data transfer between the MPU and the LCD module. DB7 can be used as a busy flag.               |
|         | A                | Power supply for LED B/L(+)   |
|         | K                | Power supply for LED B/L(-)   |

Backlight Controll




## 2.3 Timing Characteristics

- Writing data from MPU to ST7066U



- Reading data from ST7066U to MPU



- Write Mode (Writing data from MPU to ST7066U)

(VDD=5.0V±10%,VSS=0V,Ta=25°C)

| Symbol                          | Characteristics         | Test Condition  | Min. | Typ. | Max. | Unit |
|---------------------------------|-------------------------|-----------------|------|------|------|------|
| T <sub>C</sub>                  | Enable Cycle Time       | Pin E           | 1200 | -    | -    | ns   |
| T <sub>PW</sub>                 | Enable Pulse Width      | Pin E           | 140  | -    | -    | ns   |
| T <sub>R</sub> , T <sub>F</sub> | Enable Rise / Fall Time | Pin E           | -    | -    | 25   | ns   |
| T <sub>AS</sub>                 | Address Setup Time      | Pins: RS , RW,E | 0    | -    | -    | ns   |
| T <sub>AH</sub>                 | Address Hold Time       | Pins :RS,RW,E   | 10   | -    | -    | ns   |
| T <sub>DSW</sub>                | Data Setup Time         | Pins:DB0~DB7    | 40   | -    | -    | ns   |
| T <sub>H</sub>                  | Data Hold Time          | Pins:DB0~DB7    | 10   | -    | -    | ns   |

- Read Mode (Reading data from ST7066U to MPU)

(VDD=5.0V±10%,VSS=0V,Ta=25°C)

| Symbol                          | Characteristics         | Test Condition  | Min. | Typ. | Max. | Unit |
|---------------------------------|-------------------------|-----------------|------|------|------|------|
| T <sub>C</sub>                  | Enable Cycle Time       | Pin E           | 1200 | -    | -    | ns   |
| T <sub>PW</sub>                 | Enable Pulse Width      | Pin E           | 140  | -    | -    | ns   |
| T <sub>R</sub> , T <sub>F</sub> | Enable Rise / Fall Time | Pin E           | -    | -    | 25   | ns   |
| T <sub>AS</sub>                 | Address Setup Time      | Pins: RS , RW,E | 0    | -    | -    | ns   |
| T <sub>AH</sub>                 | Address Hold Time       | Pins :RS,RW,E   | 10   | -    | -    | ns   |
| T <sub>DDR</sub>                | Data Setup Time         | Pins:DB0~DB7    | -    | -    | 100  | ns   |
| T <sub>H</sub>                  | Data Hold Time          | Pins:DB0~DB7    | 10   | -    | -    | ns   |

## 2.4 Display Command

| Instructions               | Instruction Code |     |      |      |      |      |      |      |      |      | Description   | Description Time (270KHz) |
|----------------------------|------------------|-----|------|------|------|------|------|------|------|------|---|---------------------------|
|                            | RS               | R/W | DB 7 | DB 6 | DB 5 | DB 4 | DB 3 | DB 2 | DB 1 | DB 0 |   |                           |
| Clear Display              | 0                | 0   | 0    | 0    | 0    | 0    | 0    | 0    | 0    | 1    | Write "20H" to DDRAM. and set DDRAM address to "00H" from AC.   | 1.52ms                    |
| Return Home                | 0                | 0   | 0    | 0    | 0    | 0    | 0    | 0    | 1    | ×    | Set DDRAM address to "00H" from AC and return cursor to it's original position if shifted. The contents of DDRAM are not changed. | 1.52ms                    |
| Entry Mode Set             | 0                | 0   | 0    | 0    | 0    | 0    | 0    | 1    | I/D  | S    | Sets cursor move direction and specifies display shift. These operations are performed during data write and read .               | 37μs                      |
| Display ON/OFF             | 0                | 0   | 0    | 0    | 0    | 0    | 1    | D    | C    | B    | D=1 : entire display on<br>C=1 : cursor on<br>B=1 : cursor position on  | 37μs                      |
| Cursor or Display Shift    | 0                | 0   | 0    | 0    | 0    | 1    | S/C  | R/L  | ×    | ×    | Set cursor moving and display shift control bit, and the direction, without changing of DDRAM data.                               | 37μs                      |
| Function Set               | 0                | 0   | 0    | 0    | 1    | DL   | N    | F    | ×    | ×    | DL: interface data is 8/4 bits<br>NL: number of line is 2/1<br>F: font size is 5×11/5×8   | 37μs                      |
| Set CGRAM Address          | 0                | 0   | 0    | 1    | AC 5 | AC 4 | AC 3 | AC 2 | AC 1 | AC 0 | Set CGRAM address in address counter.   | 37μs                      |
| Set DDRAM Address          | 0                | 0   | 1    | AC 6 | AC 5 | AC 4 | AC 3 | AC 2 | AC 1 | AC 0 | Set DDRAM address in address counter.   | 37μs                      |
| Read Busy Flag and Address | 0                | 1   | BF   | AC 6 | AC 5 | AC 4 | AC 3 | AC 2 | AC 1 | AC 0 | Whether during internal operation or not can be known by reading BF. The contents of address counter can also be read.            | 0μs                       |

|                    |   |   |    |    |    |    |    |    |    |    |   |      |
|--------------------|---|---|----|----|----|----|----|----|----|----|---|------|
| Write Data to RAM  | 1 | 0 | D7 | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Write data into internal RAM (DDRAM/CGRAM). | 37µs |
| Read Data from RAM | 1 | 1 | D7 | D6 | D5 | D4 | D3 | D2 | D1 | D0 | Read data from internal RAM (DDRAM/CGRAM).  | 37µs |

Note:

Be sure the ST7066U is not in the busy state (BF=0) before sending an instruction from the MPU to the ST7066.

If an instruction is sent without checking the busy flag , the time between the first instruction and next instruction will take much longer than the instruction time itself.

Refer to Instruction Table for the list of each instruction execution time .


## 2.5 Character Pattern


### CHARACTER PATTERN(SO/HO/EA,WA)

| Lower 4 Bits \ Upper 4 Bits | 0000       | 0001 | 0010 | 0011 | 0100 | 0101 | 0110 | 0111 | 1000 | 1001 | 1010 | 1011 | 1100 | 1101 | 1110 | 1111 |
|-----------------------------|------------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| xxxx0000                    | CG RAM (1) |      |      | 0    | A    | P    | `    | p    |      |      |      | —    | 9    | E    | o    | P    |
| xxxx0001                    | (2)        | !    | 1    | A    | Q    | a    | a    |      |      |      | •    | 7    | +    | 4    | ä    | q    |
| xxxx0010                    | (3)        | "    | 2    | B    | R    | b    | r    |      |      |      | "    | 4    | u    | x    | p    | e    |
| xxxx0011                    | (4)        | #    | 3    | C    | S    | c    | s    |      |      |      | ∟    | ウ    | T    | E    | S    | •    |
| xxxx0100                    | (5)        | \$   | 4    | D    | T    | d    | t    |      |      |      | ∟    | エ    | ト    | +    | ノ    | Q    |
| xxxx0101                    | (6)        | %    | 5    | E    | U    | e    | u    |      |      |      | •    | オ    | +    | ∟    | o    | Q    |
| xxxx0110                    | (7)        | &    | 6    | F    | V    | f    | v    |      |      |      | ヲ    | カ    | ∟    | ヨ    | P    | Σ    |
| xxxx0111                    | (8)        | '    | 7    | G    | W    | g    | w    |      |      |      | ア    | +    | ア    | ア    | 9    | π    |
| xxxx1000                    | (1)        | (    | 8    | H    | X    | h    | x    |      |      |      | 4    | 0    | ホ    | リ    | ∟    | ア    |
| xxxx1001                    | (2)        | )    | 9    | I    | Y    | i    | y    |      |      |      | ウ    | 7    | ∟    | ∟    | ∟    | ∟    |
| xxxx1010                    | (3)        | *    | #    | J    | Z    | j    | z    |      |      |      | エ    | コ    | ∟    | ∟    | ∟    | ∟    |
| xxxx1011                    | (4)        | +    | :    | K    | C    | k    | c    |      |      |      | オ    | サ    | ∟    | ∟    | ∟    | ∟    |
| xxxx1100                    | (5)        | ,    | <    | L    | #    | l    | ∟    |      |      |      | ホ    | ヨ    | ∟    | ∟    | ∟    | ∟    |
| xxxx1101                    | (6)        | —    | =    | M    | ∟    | m    | ∟    |      |      |      | ユ    | ズ    | ∟    | ∟    | ∟    | ∟    |
| xxxx1110                    | (7)        | •    | >    | N    | ∟    | n    | ∟    |      |      |      | ヨ    | セ    | ∟    | ∟    | ∟    | ∟    |
| xxxx1111                    | (8)        | /    | ?    | O    | ∟    | o    | ∟    |      |      |      | ウ    | ∟    | ∟    | ∟    | ∟    | ∟    |

## 3. QUALITY ASSURANCE SYSTEM

### 3.1 Quality Assurance Flow Chart



| Item          | Customer   | Sales | R&D | Q.A | Manufacturing   | Product control | Purchase | Inventory control |
|---------------|--|-------|-----|-----|---|-----------------|----------|-------------------|
| Sales Service |  <pre> graph TD     Info[Info] --&gt; Claim[Claim]     Claim --&gt; FA[Failure analysis]     FA --&gt; AR[Analysis report]     FA --&gt; CA[Corrective action]     CA --&gt; Tracking[Tracking]         </pre> |       |     |     |   |                 |          |                   |
| Q.A Activity  | 1. ISO 9001 Maintenance Activities<br>3. Equipment calibration<br>5. Standardization Management  |       |     |     | 2. Process improvement proposal<br>4. Education And Training Activities |                 |          |                   |



### 3.2 Inspection Specification

Inspection Standard : MIL-STD-105E Table Normal Inspection Single Sampling Level II ◦

Equipment : Gauge 、 MIL-STD 、 Powertip Tester 、 Sample ◦


IQC Defect Level : Major Defect AQL 0.4; Minor Defect AQL 1.5 ◦

FQC Defect Level : 100% Inspection ◦

OUT Going Defect Level : Sampling ◦

Specification :

| NO   | Item   | Specification   | Judge | Level |
|--|--|---|-------|-------|
| 1  | Part Number  | The part number is inconsistent with work order of production   | N.G   | Major |
| 2  | Quantity   | The quantity is inconsistent with work order of production  | N.G   | Major |
| 3  | Electronic characteristics of LCM<br>$A=(L+W)\div 2$ | The display lacks of some patterns.   | N.G   | Major |
|  |  | Missing line.   | N.G   | Major |
|  |  | The size of missing dot, A is $> 1/2$ Dot size  | N.G   | Major |
|  |  | There is no function.   | N.G   | Major |
|  |  | Output data is error  | N.G   | Major |
| 4  | Appearance of LCD<br>$A=(L+W)\div 2$                 | Material is different with work order of production   | N.G   | Major |
|  |  | LCD is assembled in inverse direction   | N.G   | Major |
|  |  | Bezel is assembled in inverse direction   | N.G   | Major |
|  |  | Shadow is within LCD viewing area + 0.5 mm  | N.G   | Major |
|  |  | The diameter of dirty particle, A is $> 0.4$ mm   | N.G   | Minor |
|  |  | Dirty particle length is $> 3.0$ mm, and $0.01$ mm $<$ width $\leq 0.05$ mm                           | N.G   | Minor |
|  | Dirty particle (Including scratch 、 bubble )         | Display is without protective film  | N.G   | Minor |
|  |  | Conductive rubber is over bezel 1mm   | N.G   | Minor |
|  |  | Polarizer exceeds over viewing area of LCD  | N.G   | Minor |
|  |  | Area of bubble in polarizer, A $> 1.0$ mm, the number of bubble is $> 1$ piece.                       | N.G   | Minor |
|  |  | $0.4$ mm $<$ Area of bubble in polarizer, A $< 1.0$ mm, the number of bubble is $> 4$ pieces.         | N.G   | Minor |
|  |  |   |       |       |
| 5  | Appearance of PCB<br>$A=(L+W)\div 2$                 | Burned area or wrong part number is on PCB  | N.G   | Major |
|  |  | The symbol, character, and mark of PCB are unidentifiable.  | N.G   | Minor |
|  |  | The stripped solder mask , A is $> 1.0$ mm  | N.G   | Minor |
|  |  | $0.3$ mm $<$ stripped solder mask or visible circuit, A $< 1.0$ mm, and the number is $\geq 4$ pieces | N.G   | Minor |
|  |  | There is particle between the circuits in solder mask   | N.G   | Minor |
|  |  | The circuit is peeled off or cracked  | N.G   | Minor |
|  |  | There is any circuits risen or exposed.   | N.G   | Minor |
|  |  | $0.2$ mm $<$ Area of solder ball, A is $\leq 0.4$ mm  | N.G   | Minor |
| The number of solder ball is $\geq 3$ pieces | N.G  | Minor   |       |       |
|  |  |   |       |       |
|  |  | The magnitude of solder ball, A is $> 0.4$ mm.  | N.G   | Minor |

| NO | Item  | Specification   | Judge | Level |
|----|---|---|-------|-------|
| 6  | Appearance of molding<br>$A=(L+W)\div 2$                  | The shape of modeling is deformed by touching.  | N.G.  | Major |
|    |   | Insufficient epoxy: Circuit or pad of IC is visible   | N.G.  | Minor |
|    |   | Excessive epoxy: Diameter of modeling is $>20\text{mm}$ or height is $>2.5\text{mm}$                          | N.G.  | Minor |
|    |   | The diameter of pinhole in modeling, A is $>0.2\text{mm}$ .   | N.G.  | Minor |
| 7  | Appearance of frame<br>$A=(L+W)\div 2$                    | The folding angle of frame must be $>45^\circ +10^\circ$  | N.G.  | Minor |
|    |   | The area of stripped electroplate in top-view of frame, A is $>1.0\text{mm}$ .                                | N.G.  | Minor |
|    |   | Rust or crack is (Top view only)  | N.G.  | Minor |
|    |   | The scratched width of frame is $>0.06\text{mm}$ . (Top view only)  | N.G.  | Minor |
| 8  | Electrical characteristic of backlight<br>$A=(L+W)\div 2$ | The color of backlight is nonconforming   | N.G.  | Major |
|    |   | Backlight can't work normally.  | N.G.  | Major |
|    |   | The LED lamp can't work normally  | N.G.  | Major |
|    |   | The unsoldering area of pin for backlight, A is $>1/2$ solder joint area.                                     | N.G.  | Minor |
|    |   | The height of solder pin for backlight is $>2.0\text{mm}$   | N.G.  | Minor |
| 10 | Assembly parts<br>$A=(L+W)\div 2$                         | The mark or polarity of component is unidentifiable.  | N.G.  | Minor |
|    |   | The height between bottom of component and surface of the PCB is floating $>0.7\text{mm}$                     | N.G.  | Minor |
|    |   | $D > 1/4W$<br>             | N.G.  | Minor |
|    |   | End solder joint width, $D'$ is $>50\%$ width of component termination or width of pad                        | N.G.  | Minor |
|    |   | Side overhang, D is $>25\%$ width of component termination.   | N.G.  | Minor |
|    |   | Component is cracked, deformed, and burned, etc.  | N.G.  | Minor |
|    |   | The polarity of component is placed in inverse direction.   | N.G.  | Minor |
|    |   | Maximum fillet height of solder extends onto the component body or minimum fillet height is $<0.5\text{mm}$ . | N.G.  | Minor |

## 4. RELIABILITY TEST

### 4.1 Reliability Test Condition

| NO | Item                               | Test Condition  |   |
|----|------------------------------------|---|---|
| 1  | High Temperature Storage           | Storage at $80 \pm 2^{\circ}\text{C}$ 96~100 hrs<br>Surrounding temperature, then storage at normal condition 4hrs  |   |
| 2  | Low Temperature Storage            | Storage at $-30 \pm 2^{\circ}\text{C}$ 96~100 hrs<br>Surrounding temperature, then storage at normal condition 4hrs   |   |
| 3  | High Temperature /Humidity Storage | 1.Storage 96~100 hrs $60 \pm 2^{\circ}\text{C}$ , 90~95%RH surrounding temperature, then storage at normal condition 4hrs.<br>(Excluding the polarizer).<br>or<br>2.Storage 96~100 hrs $40 \pm 2^{\circ}\text{C}$ , 90~95%RH surrounding temperature, then storage at normal condition 4 hrs. |   |
| 4  | Temperature Cycling                | $-20^{\circ}\text{C} \rightarrow 25^{\circ}\text{C} \rightarrow 70^{\circ}\text{C} \rightarrow 25^{\circ}\text{C}$ $\leftarrow (30\text{mins}) (5\text{mins}) (30\text{mins}) (5\text{mins}) \rightarrow$ <p style="text-align: center;">10 Cycle</p>   |   |
| 5  | Vibration                          | 10~55Hz ( 1 minute ) 1.5mm<br>X,Y and Z direction * (each 2hrs)   |   |
| 6  | ESD Test                           | Air Discharge:<br>Apply 6 KV with 5 times discharge for each polarity +/-   | Contact Discharge:<br>Apply 250V with 5 times discharge for each polarity +/- |
|    |                                    | Testing location:<br>Around the face of LCD   | Testing location:<br>1.Apply to bezel.<br>2.Apply to Vdd, Vss.                |
| 7  | Drop Test                          | Packing Weight (Kg)   | Drop Height (cm)  |
|    |                                    | 0 ~ 45.4  | 122   |
|    |                                    | 45.4 ~ 90.8   | 76  |
|    |                                    | 90.8 ~ 454  | 61  |
|    |                                    | Over 454  | 46  |

---

## **5. PRECAUTION RELATING PRODUCT HANDLING**

### **5.1 SAFETY**

- 5.1.1 If the LCD panel breaks , be careful not to get the liquid crystal to touch your skin.
- 5.1.2 If the liquid crystal touches your skin or clothes , please wash it off immediately by using soap and water.

### **5.2 HANDLING**

- 5.2.1 Avoid any strong mechanical shock which can break the glass.
- 5.2.2 Avoid static electricity which can damage the CMOS LSI—When working with the module , be sure to ground your body and any electrical equipment you may be using.
- 5.2.3 Do not remove the panel or frame from the module.
- 5.2.4 The polarizing plate of the display is very fragile. So , please handle it very carefully ,do not touch , push or rub the exposed polarizing with anything harder than an HB pencil lead (glass , tweezers , etc.)
- 5.2.5 Do not wipe the polarizing plate with a dry cloth , as it may easily scratch the surface of plate.
- 5.2.6 Do not touch the display area with bare hands , this will stain the display area.
- 5.2.7 Do not use ketonics solvent & aromatic solvent. Use with a soft cloth soaked with a cleaning naphtha solvent.
- 5.2.8 To control temperature and time of soldering is  $280\pm 10^{\circ}\text{C}$  and 3-5 sec.
- 5.2.9 To avoid liquid (include organic solvent) stained on LCM .

### **5.3 STORAGE**

- 5.3.1 Store the panel or module in a dark place where the temperature is  $25^{\circ}\text{C} \pm 5^{\circ}\text{C}$  and the humidity is below 65% RH.
- 5.3.2 Do not place the module near organics solvents or corrosive gases.
- 5.3.3 Do not crush , shake , or jolt the module.

### **5.4 TERMS OF WARRANTY**

- 5.4.1 Applicable warrant period  
The period is within thirteen months since the date of shipping out under normal using and storage conditions.
- 5.4.2 Unaccepted responsibility  
This product has been manufactured to your company's specification as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment , we cannot take responsibility if the product is used in nuclear power control equipment , aerospace equipment , fire and security systems or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required.