

---

# cDAQ-9133

# Specifications

---

2022-06-30



# Contents

cDAQ-9133 Specifications..... 3

# cDAQ-9133 Specifications

These specifications are for the cDAQ-9133 controller only. These specifications are typical at 23 °C ±5 °C unless otherwise noted. For the C Series module specifications, refer to the documentation for the C Series module you are using.

## Processor

CPU	Intel Atom E3825
Number of cores	2
CPU frequency	1.33 GHz
On-die L2 cache	1 MB (shared)

## Operating System

Supported operating systems	Windows Embedded Standard 7 (WES7), NI Linux Real-Time
-----------------------------	--

## Network/Ethernet Port

Number of ports	2
Network interface	10Base-T, 100Base-TX, and 1000Base-T Ethernet
Compatibility	IEEE 802.3
Communication rates	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s/auto-negotiated

Maximum cabling distance	100 m/segment
--------------------------	---------------

## RS-232 Serial Port

Maximum baud rate	115,200 bps
Data bits	5, 6, 7, 8
Stop bits	1, 2
Parity	Odd, even, mark, space
Flow control	RTS/CTS, XON/XOFF, DTR/DSR
RI wake maximum low level	0.8 V
RI wake minimum high level	2.4 V
RI overvoltage tolerance	±24 V

## USB Ports

<b>Number of ports</b>	
Device ports	1 standard B connector
Host ports	2 standard A connectors



**Note** The USB device port is intended for use in device configuration, application deployment, debug, and maintenance.

USB interface	USB 2.0, Hi-Speed
Maximum data rate	480 Mb/s
Maximum current (USB host ports)	1 A (aggregate)

## Mini DisplayPort

Maximum resolution	2560 × 1600 at 60 Hz
--------------------	----------------------

## SD Card Slot

SD card support	SD and SDHC standards
-----------------	-----------------------

## Memory

<b>Nonvolatile<sup>[1]</sup></b>	
SD removable (user supplied)	Up to 32 GB
SSD	16 GB
System memory	2 GB DDR3L



**Note** For information about the life span of the nonvolatile memory and about best practices for using nonvolatile memory, go to [ni.com/info](http://ni.com/info) and enter Info Code ssdbp.

## Data throughput

System memory to SD removable storage <sup>[2],[3]</sup>	10 MB/s
Module slots to system memory	20 MB/s, application and system dependent

## Internal Real-Time Clock

Accuracy	200 ppm; 40 ppm at 25 °C
----------	--------------------------

## CMOS Battery

Typical battery life with power applied to power connector	10 years
Typical battery life when stored at temperatures up to 25 °C	7.8 years
Typical battery life when stored at temperatures up to 85 °C	5.4 years

## Analog Input

Input FIFO size	127 samples per slot
Maximum sample rate <sup>[4]</sup>	Determined by the C Series module or modules
Timing accuracy <sup>[5]</sup>	50 ppm of sample rate
Timing resolution <sup>[5]</sup>	12.5 ns
Number of channels supported	Determined by the C Series module or modules

## Analog Output

<b>Number of channels supported</b>	
<b>Hardware-timed task</b>	
Onboard regeneration	16
Non-regeneration	Determined by the C Series module or modules
Non-hardware-timed task	Determined by the C Series module or modules
<b>Maximum update rate</b>	
Onboard regeneration	1.6 MS/s (multi-channel, aggregate)
Non-regeneration	Determined by the C Series module or modules
Timing accuracy	50 ppm of sample rate
Timing resolution	12.5 ns
<b>Output FIFO size</b>	
Onboard regeneration	8,191 samples shared among channels used
Non-regeneration	127 samples per slot
AO waveform modes	Non-periodic waveform,  periodic waveform regeneration mode from onboard memory,  periodic waveform regeneration from host buffer including dynamic update

## Digital Waveform Characteristics

### Waveform acquisition (DI) FIFO

Parallel modules	511 samples per slot
Serial modules	63 samples per slot

### Waveform generation (DO) FIFO

#### Parallel modules

Slots 1 to 4	2,047 samples per slot
Slots 5 to 8	1,023 samples per slot
Serial modules	63 samples per slot



**Note** When parallel modules in a digital task are in slots 1 through 4, FIFO is 2,047 samples per slot for all slots. When any parallel module in a digital task is in slots 5 through 8, FIFO is 1,023 samples per slot for all eight slots.

### Digital input sample clock frequency

Streaming to application memory	System-dependent
Finite	0 MHz to 10 MHz

### Digital output sample clock frequency

Streaming from application memory	System-dependent
Regeneration from FIFO	0 MHz to 10 MHz



Finite	0 MHz to 10 MHz
Timing accuracy	50 ppm

## General-Purpose Counters/Timers

Number of counters/timers	4
Resolution	32 bits
Counter measurements	Edge counting, pulse, semi-period, period, two-edge separation, pulse width
Position measurements	X1, X2, X4 quadrature encoding with Channel Z reloading; two-pulse encoding
Output applications	Pulse, pulse train with dynamic updates, frequency division, equivalent time sampling
Internal base clocks	80 MHz, 20 MHz, 100 kHz
External base clock frequency	0 MHz to 20 MHz
Base clock accuracy	50 ppm
Output frequency	0 MHz to 20 MHz
Inputs	Gate, Source, HW_Arm, Aux, A, B, Z, Up_Down
Routing options for inputs	Any module PFI, controller PFI, analog trigger, many internal signals

FIFO	Dedicated 127-sample FIFO
------	---------------------------

## Frequency Generator

Number of channels	1
Base clocks	20 MHz, 10 MHz, 100 kHz
Divisors	1 to 16 (integers)
Base clock accuracy	50 ppm
Output	Any controller PFI or module PFI terminal

## Module PFI Characteristics

Functionality	Static digital input, static digital output, timing input, and timing output
Timing output sources <sup>[6]</sup>	Many analog input, analog output, counter, digital input, and digital output timing signals
Timing input frequency	0 MHz to 20 MHz
Timing output frequency	0 MHz to 20 MHz

## Controller PFI Characteristics

Maximum input or output frequency	1 MHz
-----------------------------------	-------

Cable length	3 m (10 ft)
Cable impedance	50 $\Omega$
PFI 0 connector	SMB
Power-on state	High impedance

Table 3. Input/Output Voltage Protection

Voltage	Minimum	Maximum
Input	-20 V	25 V
Output	-15 V	20 V

**Maximum operating conditions<sup>[7]</sup>**

$I_{OL}$ output low current	8 mA maximum
$I_{OH}$ output high current	-8 mA maximum

Table 3. DC Input Characteristics

Voltage	Minimum	Maximum
Positive going threshold	1.43 V	2.28 V
Negative going threshold	0.86 V	1.53 V
Hysteresis	0.48 V	0.87 V

Table 3. DC Output Characteristics

Voltage	Conditions	Minimum	Maximum
High	—	—	5.25 V
	Sourcing 100 $\mu$ A	4.65 V	—
	Sourcing 2 mA	3.60 V	—
	Sourcing 3.5 mA	3.44 V	—
Low	Sinking 100 $\mu$ A	—	0.10 V
	Sinking 2 mA	—	0.64 V

Voltage	Conditions	Minimum	Maximum
	Sinking 3.5 mA	—	0.80 V

## Digital Triggers

Source	Any controller PFI or module PFI terminal
Polarity	Software-selectable for most signals
Analog input function	Start Trigger, Reference Trigger, Pause Trigger, Sample Clock, Sample Clock Timebase
Analog output function	Start Trigger, Pause Trigger, Sample Clock, Sample Clock Timebase
Counter/timer function	Gate, Source, HW_Arm, Aux, A, B, Z, Up_Down

## Module Data Interface

High-performance data streams	7
Data stream types available	Analog input, analog output, digital input, digital output, counter/timer input, counter/timer output, NI-XNET <sup>[8]</sup>

## Module I/O States

At power-on	Module-dependent. Refer to the documentation for each C Series module.
-------------	--

## Power Requirements



**Note** Some C Series modules have additional power requirements. For more information about C Series module power requirements, refer to the C Series module(s) documentation.



**Note** Sleep mode for C Series modules is not supported in the cDAQ-9133.

Voltage input range	9 to 30 V (measured at the cDAQ-9133 power connector)
Maximum power consumption <sup>[9]</sup>	46 W



**Note** The maximum power consumption specification is based on a fully populated system running a high-stress application at elevated ambient temperature, and with all C Series modules and USB devices consuming the maximum allowed power.

Typical standby power consumption	3.4 W at 24 VDC input
Recommended power supply	100 W, 24 VDC

### Typical leakage current from secondary power input (V2) while system is powered from primary power input (V1)

At 9 V	0.40 mA
At 30 V	1.93 mA



**Caution** Do not connect V2 to a DC MAINS supply or to any supply requiring a connecting cable longer than 3 m (10 ft). A DC MAINS supply

is a local DC electricity supply network in the infrastructure of a site or building.

### EMC ratings for inputs as described in IEC 61000

V1 Short lines, long lines, and DC distributed networks

V2 Short lines only

Power input connector	4 position 3.5 mm pitch pluggable screw terminal with screw locks, Sauro CTF04BV8-AN000A
-----------------------	--

## Physical Characteristics


Weight (unloaded)	2.5 kg (5 lb 8.2 oz)
Dimensions (unloaded)	328.8 mm × 88.1 mm × 118.6 mm (12.95 in. × 3.47 in. × 4.67 in.) Refer to the following figure.
Gauge	0.5 mm <sup>2</sup> to 2.1 mm <sup>2</sup> (20 AWG to 14 AWG) copper conductor wire
Wire strip length	6 mm (0.24 in.) of insulation stripped from the end
Temperature rating	85 °C
Torque for screw terminals	0.20 N · m to 0.25 N · m (1.8 lb · in. to 2.2 lb · in.)
Wires per screw terminal	One wire per screw terminal

### Connector securement

Securement type                      Screw flanges provided

Torque for screw flanges 0.20 N · m to 0.25 N · m (1.8 lb · in. to 2.2 lb · in.)

Figure 1. cDAQ-9133 Dimensions



## Safety Voltages

Connect only voltages that are below these limits.

V1 terminal to C terminal	30 VDC maximum, Measurement Category I
V2 terminal to C terminal	30 VDC maximum, Measurement Category I

Chassis ground to C terminal	30 VDC maximum, Measurement Category I
------------------------------	--

Measurement Category I is for measurements performed on circuits not directly connected to the electrical distribution system referred to as MAINS voltage. MAINS is a hazardous live electrical supply system that powers equipment. This category is for measurements of voltages from specially protected secondary circuits. Such voltage measurements include signal levels, special equipment, limited-energy parts of equipment, circuits powered by regulated low-voltage sources, and electronics.



**Caution** Do not connect the cDAQ-9133 to signals or use for measurements within Measurement Categories II, III, or IV.



**Attention** FR translation TBD.



**Note** Measurement Categories CAT I and CAT O are equivalent. These test and measurement circuits are for other circuits not intended for direct connection to the MAINS building installations of Measurement Categories CAT II, CAT III, or CAT IV.

## Environmental

### Temperature (IEC 60068-2-1 and IEC 60068-2-2)

Operating -20 to 55 °C

Storage -40 to 85 °C



**Caution** Failure to follow the mounting instructions in the **cDAQ-9132/9133/9134/9135/9136/9137 User Manual** can cause temperature derating. For more information about mounting




configurations and temperature derating, go to [ni.com/info](http://ni.com/info) and enter Info Code `cdaqmounting`.



**Caution** To maintain product performance and accuracy specifications when the ambient temperature is -20 to 55 °C, you must mount the controller horizontally to a metal panel or surface using the screw holes or the panel mount kit. Measure the ambient temperature at each side of the CompactDAQ system 63.5 mm (2.5 in.) from the side and 38.1 mm (1.50 in.) from the rear cover of the system. For further information about mounting configurations, go to [ni.com/info](http://ni.com/info) and enter the Info Code `cdaqmounting`.

Figure 1. cDAQ-9133 Temperature, Cooling, and Cabling Dimensions



**Humidity (IEC 60068-2-56)**

Operating 10 to 90% RH, noncondensing

Storage 5 to 95% RH, noncondensing

Ingress protection

IP 30

Pollution Degree (IEC 60664)

2

Maximum altitude	5,000 m
------------------	---------

Indoor use only.

## Hazardous Locations

U.S. (UL)	Class I, Division 2, Groups A, B, C, D, T4; Class I, Zone 2, AEx nA IIC T4
Canada (C-UL)	Class I, Division 2, Groups A, B, C, D, T4; Class I, Zone 2, Ex nA IIC T4
Europe (DEMKO)	Ex nA IIC T4 Gc

## Shock and Vibration

To meet these specifications, you must mount the cDAQ-9133 system directly on a flat, rigid surface as described in the **cDAQ-9132/9133/9134/9135/9136/9137 User Manual**, affix ferrules to the ends of the terminal wires, install an SD card cover (SD Door Kit, NI part number 783660-01), and use retention accessories for the USB host ports (NI Industrial USB Extender Cable, NI part number 152166-xx), USB device port (NI Locking USB Cable, NI part number 157788-01), and mini DisplayPort connector (NI Retention Accessory for Mini DisplayPort, NI part number 156866-01). All cabling should be strain relieved near input connectors. Take care to not directionally bias cable connectors within input connectors when applying strain relief.

<b>Operating vibration</b>	
Random	5 g RMS, 10 Hz to 500 Hz
Sinusoidal	5 g, 10 Hz to 500 Hz
Operating shock	30 g, 11 ms half sine,

	50 g, 3 ms half sine,  18 shocks at 6 orientations
--	--

## Safety Compliance and Hazardous Locations Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1
- EN 60079-0, EN 60079-7
- IEC 60079-0, IEC 60079-7
- UL 60079-0, UL 60079-7
- CSA C22.2 No. 60079-0, CSA C22.2 No. 60079-7



**Note** For safety certifications, refer to the product label or the [Product Certifications and Declarations](#) section.

## Electromagnetic Compatibility

## CE Compliance

- 2014/34/EU; Potentially Explosive Atmospheres (ATEX)

## Product Certifications and Declarations


Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit [ni.com/product-certifications](https://ni.com/product-certifications), search by model number, and click the appropriate link.

## Environmental Management


NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the **Engineering a Healthy Planet** web page at [ni.com/environment](http://ni.com/environment). This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

### EU and UK Customers

-  Waste Electrical and Electronic Equipment (WEEE)—At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit [ni.com/environment/weee](http://ni.com/environment/weee).

### Battery Replacement and Disposal

-  Battery Directive—This product contains a long-life coin cell battery. If you need to replace it, use the Return Material Authorization (RMA) process or contact an authorized NI service representative. For more information about compliance with the EU Battery Directive 2006/66/EC about Batteries and Accumulators and Waste Batteries and Accumulators, visit [ni.com/environment/batterydirective](http://ni.com/environment/batterydirective).

### 电子信息产品污染控制管理办法 ( 中国 RoHS )

-  中国 RoHS—NI 符合中国电子信息产品中限制使用某些有害物质指令(RoHS)。关于 NI 中国 RoHS 合规性信息，请登录 [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china)。(For information about China RoHS compliance, go to [ni.com/environment/rohs\\_china](http://ni.com/environment/rohs_china).)

- <sup>1</sup> 1 MB is equal to 1 million bytes. 1 GB is equal to 1 billion bytes; formatted capacity might be less.
- <sup>2</sup> Go to [ni.com/info](http://ni.com/info) and enter Info Code exyerk for information about best practices for data logging performance with the cDAQ-9133.
- <sup>3</sup> Consult the SD removable storage manufacturer specifications.
- <sup>4</sup> Performance dependent on type of installed C Series module and number of channels in the task.
- <sup>5</sup> Does not include group delay. For more information, refer to the documentation for each C Series module.
- <sup>6</sup> Actual available signals are dependent on type of installed C Series module.
- <sup>7</sup> Stresses beyond those listed under **Maximum operating conditions** may cause permanent damage to the controller.
- <sup>8</sup> When a session is active, CAN or LIN (NI-XNET) C Series modules use a total of two data streams regardless of the number of NI-XNET modules in the controller.
- <sup>9</sup> Includes maximum 1 W module load per slot across rated temperature and product variations.