


# PXIe-SMU5102 Bundle

Expandable PXI bundle based on PXIe-4137 SMU, ±200 V, ±1 A DC, ±3 A Pulsed, 20 W DC, 100 fA

**Specifications** 

PXIe-1083 and PXIe-4137




# PXI SMU Bundle

#### In the Box



#### **Recommended Software**



#### Table of Contents

This document combines the PDFs of this bundle together. The page numbers in the table of contents correspond to the page number of PDF the component's documentation begins.

PXIe-1083 Specifications	3
PXIe-4137 Specifications	16

# PXIe-1083 Specifications





# PXIe-1083 Specifications

This document contains specifications for the PXIe-1083 chassis.

## Electrical

The following section provides information about the PXIe-1083 AC input and DC output.

#### AC Input

Input rating	100 VAC to 240 VAC, 50 Hz/60 Hz, 6 A to 3 A
Operating voltage range <sup>1</sup>	90 VAC to 264 VAC
Nominal input frequency	50 Hz/60 Hz
Operating frequency range <sup>1</sup>	47 Hz to 63 Hz
Efficiency	78% typical
Over-current protection	Internal fuse in line
Main power disconnect	The AC power cable provides main power disconnect. Do not position the equipment so that it is difficult to disconnect the power cord. The front-panel power switch causes the internal chassis power supply to provide DC power to the PXI Express backplane.



Caution Disconnect power cord to completely remove power.

#### DC Output

#### DC output characteristics of the PXIe-1083.

Voltage Rail	Maximum Current	Load Regulation	Maximum Ripple and Noise (20 MHz BW)
+5V_AUX	1.0 A	±5%	50 mVpp
+12 V	30.1 A	±5%	120 mVpp
+5 V	25.1 A	±5%	50 mVpp
+3.3 V	30.7 A	±5%	50 mVpp
-12 V	0.75 A	±5%	120 mVpp

Maximum total available power for the PXIe-1083 is 293 W.

The maximum combined power available on +3.3 V and +5 V is 180 W.

The maximum power available for each Thunderbolt port is 15 W (5 V/3 A).

#### Table 1. Backplane Slot Current Capacity

Slot	+5 V	V (I/O)	+3.3 V	+12 V	-12 V	5 V <sub>AUX</sub>
Hybrid Peripheral Slot with PXI-5 Peripheral	-	-	3 A	6 A	-	1 A
Hybrid Peripheral Slot with PXI-1 Peripheral	6 A	5 A	6 A	1 A	1 A	-

**Note** PCI V(I/O) pins in Hybrid Peripheral Slots are connected to +5 V.

Note The maximum power dissipated in a peripheral slot should not exceed 58 W. Refer to the **Operating Environment** section for ambient temperature considerations at 58 W.

Over-current protection	All outputs are protected from short circuit and overload, they recover and return to regulation when the overload is removed and the power is cycled.
Over-voltage protection	+3.3 V clamped at 3.7 V to 4.3 V, +5 V clamped at 5.7 V to 6.5 V, +12 V clamped at 13.4 V to 15.6 V

# Chassis Cooling

Module cooling	Forced air circulation (positive pressurization) through one 150 CFM fan
Module slot airflow direction	Bottom of module to top of module
Module intake	Bottom of chassis
Module exhaust	Top, right side of chassis
Slot cooling capacity	58 W; slot 6 supports 58 W cooling with high fan mode
Power supply cooling	Forced air circulation through integrated fans
Power supply intake	Front and left side chassis
Power supply exhaust	Rear of chassis
Minimum chassis cooling cl	earances
Above	44.45 mm (1.75 in.)
Rear	44.45 mm (1.75 in.)
Sides	44.45 mm (1.75 in.)
Below	
Rack	44.45 mm (1.75 in.)
Desktop	25.4 mm (1.00 in.)

## Environmental

Maximum altitude	2,000 m (6,560 ft.), 800 mbar (at 25 °C ambient, high fan mode)
Pollution Degree	2

Indoor use only.

## Operating Environment

Ambient temperature range	
When all peripheral modules	0 °C to 50 °C (IEC 60068-2-1 and IEC 60068-2-2.) <sup>2</sup> Meets
require ≤38 W cooling capacity	MIL-PRF-28800F Class 3 low temperature limit and high
per slot	temperature limit.
When any peripheral module	0 °C to 40 °C (IEC 60068-2-1 and IEC 60068-2-2.) <sup>2</sup> Meets
requires >38 W cooling capacity	MIL-PRF-28800F Class 3 low temperature limit and MIL-
per slot	PRF-28800F Class 4 high temperature limit.
Relative humidity range	20% to 80%, noncondensing

## Storage Environment

Ambient temperature range	–40 °C to 71 °C (IEC-60068-2-1 and IEC-60068-2-2.) <sup>[3]</sup> Meets MIL- PRF-28800F Class 3 limits.
Relative humidity range	10% to 95%, noncondensing

## Shock and Vibration

Operational shock	30 g peak, half-sine, 11 ms pulse (IEC-60068-2-27.) <sup>3</sup> Meets MIL- PRF-28800F Class 2 limits.
Operational random vibration	5 to 500 Hz, 0.3 g <sub>rms</sub>
Non-operating vibration	5 to 500 Hz, 2.4 g <sub>rms</sub> (IEC 60068-2-64.) <sup>3</sup> Non-operating test profile exceeds the requirements of MIL-PRF-28800F, Class 3.

## Acoustic Emissions

#### Sound Pressure Level (at Operator Position)

(Tested in accordance with ISO 7779. Meets MIL-PRF-28800F requirements.)

38 W Profile	
Auto fan (up to 30 °C ambient)	33.7 dBA
High fan	50.8 dBA
58 W Profile	
Auto fan (up to 30 °C ambient)	54.7 dBA
High fan	55.3 dBA

#### Sound Power Level

#### 38 W Profile

Auto fan (up to 30 °C ambient)	44.9 dBA
High fan	60.3 dBA
58 W Profile	
Auto fan (up to 30 °C ambient)	63.4 dBA

Note The protection provided by the PXIe-1083 can be impaired if it is used in a manner not described in this document.

## Safety Compliance Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1

Note For safety certifications, refer to the product label or the <u>Product</u> <u>Certifications and Declarations</u> section.

## **EMC Guidelines**

This product was tested and complies with the regulatory requirements and limits for electromagnetic compatibility (EMC) stated in the product specifications. These requirements and limits provide reasonable protection against harmful interference when the product is operated in the intended operational electromagnetic environment. This product is intended for use in industrial locations. However, harmful interference may occur in some installations, when the product is connected to a peripheral device or test object, or if the product is used in residential areas. To minimize interference with radio and television reception and prevent unacceptable performance degradation, install and use this product in strict accordance with the instructions in the product documentation.

Furthermore, any changes or modifications to the product not expressly approved by NI could void your authority to operate it under your local regulatory rules.

#### **EMC** Notices

Refer to the following notices for cables, accessories, and prevention measures necessary to ensure the specified EMC performance.

## Notice

For EMC declarations and certifications, and additional information, refer to the <u>Product Certifications and Declarations</u> section.

**Notice** Changes or modifications to the product not expressly approved by NI could void your authority to operate the product under your local regulatory rules.

Notice Operate this product only with shielded cables and accessories.

#### **Electromagnetic Compatibility Standards**

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions

AS/NZS CISPR 11: Group 1, Class A emissions

**Note** Group 1 equipment (per CISPR 11) is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



**Note** In Europe, Canada, Australia, and New Zealand (per CISPR 11) Class A equipment is intended for use in nonresidential locations.

# CE Compliance C $\in$

This product meets the essential requirements of applicable European Directives, as follows:

- 2014/35/EU; Low-Voltage Directive (safety)
- 2014/30/EU; Electromagnetic Compatibility Directive (EMC)
- 2011/65/EU; Restriction of Hazardous Substances (RoHS)

## **Product Certifications and Declarations**

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit <u>ni.com/product-certifications</u>, search by model number, and click the appropriate link.

## **Environmental Management**

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the **Engineering a Healthy Planet** web page at <u>ni.com/environment</u>. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

#### EU and UK Customers

• A Waste Electrical and Electronic Equipment (WEEE)—At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit <u>ni.com/environment/weee</u>.

#### 电子信息产品污染控制管理办法(中国 RoHS)

• ◎ ◎ ● 中国 RoHS— NI 符合中国电子信息产品中限制使用某些有害物 质指令(RoHS)。关于 NI 中国 RoHS 合规性信息,请登录 ni.com/environment/ rohs\_china。(For information about China RoHS compliance, go to ni.com/ environment/rohs\_china.)

## Backplane

Size	3U-sized; 5 peripheral slots. Compliant with IEEE 1101.10 mechanical packaging. PXI Express Specification compliant. Accepts both PXI Express and CompactPCI (PICMG 2.0 R 3.0) 3U modules.
Backplane bare-board material	UL 94 V-0 Recognized
Backplane connectors	Conforms to IEC 917 and IEC 1076-4-101, UL 94 V-0 rated

#### System Synchronization Clocks

#### 10 MHz System Reference Clock: PXI\_CLK10

Maximum slot-to-slot skew	250 ps
Accuracy	±25 ppm max (guaranteed over the operating temperature range)
Maximum jitter	5 ps RMS phase-jitter (10 Hz–1 MHz range)
Duty-factor	45% to 55%
Unloaded signal swing	3.3 V ±0.3 V



Note For other specifications, refer to the PXI-1 Hardware Specification.

#### 100 MHz System Reference Clock: PXIe\_CLK100 and PXIe\_SYNC100

Maximum slot-to-slot skew	100 ps
Accuracy	±25 ppm max (guaranteed over the operating temperature range)
Maximum jitter	3 ps RMS phase-jitter (10 Hz to 12 kHz range), 2 ps RMS phase-jitter (12 kHz to 20 MHz range)
Duty-factor for PXIe_CLK100	45% to 55%
Absolute differential voltage (When terminated with a 50 Ω load to 1.30 V or Thévenin equivalent)	400 mV to 1000 mV




# Note For other specifications, refer to the PXI-5 PXI Express Hardware Specification.


## Mechanical

Standard chassis	dimensions
Height	177.1 mm (6.97 in.)
Width	257.1 mm (10.12 in.)
Depth	214.2 mm (8.43 in.)
Weight	6.7 kg (14.8 lb)
Chassis materials	Extruded Aluminum (6063-T5, 6060-T6), Cold Rolled Steel/Stainless Steel, Santoprene, Urethane Foam, PC-ABS, Nylon, Polyethylene
Finish	Conductive Clear Iridite on Aluminum, Electroplated Nickel on Cold Rolled Steel, Electroplated Zinc on Cold Rolled Steel

The following figures show the PXIe-1083 chassis dimensions. The holes shown are for installing the optional rack mount kits.

#### Figure 1. PXIe-1083 Chassis Dimensions (Front)





#### Figure 2. PXIe-1083 Chassis Dimensions (Side)

<sup>1</sup> The operating range is guaranteed by design.

<sup>2</sup> This product meets the requirements of the environmental standards for electrical equipment for measurement, control, and laboratory use.

<sup>3</sup> This product meets the requirements of the environmental standards for electrical equipment for measurement, control, and laboratory use.

# PXIe-4137 Specifications



# PXIe-4137 Specifications

These specifications apply to the PXIe-4137.

**Note** In this document, the PXIe-4137 (40W) and PXIe-4137 (20W) are referred to inclusively as the PXIe-4137. The information in this document applies to all versions of the PXIe-4137 unless otherwise specified. To determine which version of the module you have, locate the device name in one of the following places:

- In MAX—The PXIe-4137 (40W) shows NI PXIe-4137 (40W), and the PXIe-4137 (20W) shows as NI PXIe-4137.
- Device front panel—The PXIe-4137 (40W) shows PXIe-4137 40W
   System SMU, and the PXIe-4137 (20W) shows NI PXIe-4137 Precision
   System SMU on the front panel.

## Definitions

**Warranted** specifications describe the performance of a model under stated operating conditions and are covered by the model warranty.

**Characteristics** describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- **Typical** specifications describe the performance met by a majority of models.
- **Nominal** specifications describe an attribute that is based on design, conformance testing, or supplemental testing.
- **Measured** specifications describe the measured performance of a representative model.

Specifications are **Warranted** unless otherwise noted.

## Conditions

Specifications are valid under the following conditions unless otherwise noted.

- Ambient temperature<sup>[1]</sup> of 23 °C ± 5 °C
- Chassis with slot cooling capacity  $\ge 38 \text{ W}^{[2]}$ 
  - For chassis with slot cooling capacity = 38 W, fan speed set to HIGH
- Calibration interval of 1 year
- 30 minutes warm-up time
- Self-calibration performed within the last 24 hours
- NI-DCPower Aperture Time is set to 2 power-line cycles (PLC)

## **Cleaning Statement**

**Notice** Clean the hardware with a soft, nonmetallic brush. Make sure that the hardware is completely dry and free from contaminants before returning it to service.


## **Device Capabilities**

The following table and figure illustrate the voltage and the current source and sink ranges of the PXIe-4137.


Table 1. Current Source and Sink Ranges

DC voltage ranges	DC current source and sink ranges
<ul> <li>600 mV</li> <li>6 V</li> <li>20 V</li> </ul>	<ul> <li>1 μA</li> <li>10 μA</li> <li>100 μA</li> </ul>
■ 200 V [ <u>3]</u>	<ul> <li>1 mA</li> <li>10 mA</li> <li>100 mA</li> </ul>

DC voltage ranges DC current source and sink ranges	
	• 1 A
	• 3 A [4]



For additional information related to the Pulse Voltage or Pulse Current settings of the Output Function, for the PXIe-4137 (40W), including pulse on time and duty cycle limits for a particular operating point, refer to <u>Pulsed Operation</u>. For supplementary examples, refer to <u>Examples of Determining Extended Range Pulse</u> <u>Parameters and Optimizing Slew Rate using NI SourceAdapt</u>.



#### Figure 2. Quadrant Diagram for PXIe-4137 (20W)

DC sourcing power and sinking power are limited to the values in the following table, regardless of output voltage.  $\frac{[5]}{2}$ 

Table 2. DC Sourcing & Sinking Power

Model Variant	Chassis Type	DC Sourcing Power	DC Sinking Power
PXIe-4137 (40W)	≥58 W Slot Cooling Capacity	40 W	40 W
	<58 W Slot Cooling Capacity	20 W	12 W
PXIe-4137 (20W)	≥58 W Slot Cooling Capacity	20 W	12 W
	<58 W Slot Cooling Capacity	20 W	12 W

**Caution** Limit DC power sinking to 12 W where applicable as indicated in the above table. For <58 W cooling slots,

- Additional derating applies to sinking power when operating at an ambient temperature of >45 °C.
- If the PXI Express chassis has multiple fan speed settings, set the fans to the highest setting.

#### Related reference

Sinking Power vs. Ambient Temperature Derating

- Extended Range Pulsing for PXIe-4137 (40W)(15)
- Extended Range Pulsing for PXIe-4137 (20W)(20)

## Voltage

#### Table 3. Voltage Programming and Measurement Accuracy/Resolution

Range	(noise to 10 Hz	Noise (0.1 Hz to 10 Hz, peak			voltage + offset)/°C,
limited) to peak), Typical T <sub>cal</sub> ±5 °C [	T <sub>cal</sub> ±5 °C [7]	T <sub>cal</sub> ±1 °C [7]	0 °C to 55 °C		
600 mV	100 nV	2 μV	0.020% + 50 μV	0.017% + 30 μV	0.0005% + 1 μV
6 V	1 μV	6 μV	0.020% + 320 μV	0.017% + 90 μV	
20 V	10 µV	20 μV	0.022% + 1 mV	0.017% + 400 μV	
200 V	100 μV	200 μV	0.025% + 10 mV	0.020% + 2.5 mV	

#### Related reference

- Noise
- Load Regulation
- <u>Remote Sense</u>

#### Current

#### Table 4. Current Programming and Measurement Accuracy/Resolution

Range Resolution (noise	Noise (0.1 Hz to 10 Hz,	Accuracy (23 °C ± 5 °C) ± (% of current + offset)		Tempco ± (% of current +	
	limited) peak to peak), Typical	peak),	T <sub>cal</sub> ± 5 °C [8]	$T_{cal} \pm 1 \degree C \frac{[8]}{}$	offset)/°C, 0 °C to 55 °C
1 μA	100 fA	4 pA	0.03% + 100 pA	0.022% + 40 pA	0.0006% + 4 pA
10 µA	1 pA	30 pA	0.03% + 700 pA	0.022% + 300 pA	0.0006% + 22 pA
100 µA	10 pA	200 pA	0.03% + 6 nA	0.022% + 2 nA	0.0006% + 200 pA
1 mA	100 pA	2 nA	0.03% + 60 nA	0.022% + 20 nA	0.0006% + 2 nA
10 mA	1 nA	20 nA	0.03% + 600 nA	0.022% + 200 nA	0.0006% + 20 nA
100 mA	10 nA	200 nA	0.03% + 6 μA	0.022% + 2 μA	0.0006% + 200 nA


Range	(noise to 10 Hz,	Accuracy (23 °C ± 5 °C) ± (% of current + offset)		Tempco ± (% of current +	
	limited)	peak to peak), Typical	T <sub>cal</sub> ± 5 °C [8]	$T_{cal} \pm 1 ^{\circ}C ^{[8]}$	offset)/°C, 0 °C to 55 °C
1 A	100 nA	2 μΑ	0.04% + 60 μA	0.035% + 20 μA	0.0006% + 2 μA
3 A <sup>[9]</sup>	1 μA	20 µA	0.08% + 900 μA	0.075% + 600 μA	0.0018% + 20 μA

#### Noise

<20 mV peak-to-peak in 20 V range, device configured for normal transient response, 10 Hz to 20 MHz, typical


The following figures illustrate measurement noise as a function of measurement aperture for the PXIe-4137.

#### Figure 1. Voltage Measurement Noise vs. Measurement Aperture, Nominal



**Note** When the aperture time is set to 2 power-line cycles (PLCs), measurement noise differs slightly depending on whether the Power Line Frequency is set to 50 Hz or 60 Hz.

Figure 1. Current Measurement Noise vs. Measurement Aperture, Nominal



Note When the aperture time is set to 2 power-line cycles (PLCs), measurement noise differs slightly depending on whether the Power Line Frequency is set to 50 Hz or 60 Hz.

#### Related reference

Voltage

## Sinking Power vs. Ambient Temperature Derating

The following figure illustrates sinking power derating as a function of ambient temperature.

This applies to the PXIe-4137 (20W) when used with any chassis and only applies to the PXIe-4137 (40W) when used with a chassis with slot cooling capacity <58 W.




Figure 1. Sinking Power vs. Ambient Temperature Derating

Note When using the PXIe-4137 (40W) with a chassis with slot cooling capacity ≥58 W, ambient temperature derating does not apply.

Related reference

<u>Device Capabilities</u>

## **Output Resistance Programming Accuracy**

Current Level/ Limit Range	Programmable Resistance Range, Voltage Mode	Programmable Resistance Range, Current Mode	Accuracy ± (% of resistance setting), T <sub>cal</sub> ± 5 °C [10]
1 μΑ	0 to ±5 MΩ	$\pm 5 \text{ M}\Omega$ to $\pm \text{infinity}$	0.03%
10 µA	0 to ±500 kΩ	±500 k $\Omega$ to ±infinity	
100 µA	0 to ±50 kΩ	$\pm 50$ kΩ to $\pm infinity$	
1 mA	0 to ±5 kΩ	±5 kΩ to ±infinity	
10 mA	0 to ±500 Ω	$\pm 500 \Omega$ to $\pm infinity$	
100 mA	0 to ±50 Ω	$\pm 50 \Omega$ to $\pm infinity$	
1 A	0 to ±5 Ω	$\pm 5 \Omega$ to $\pm infinity$	

Current Level/ Limit Range	Programmable Resistance Range, Voltage Mode	Programmable Resistance Range, Current Mode	Accuracy ± (% of resistance setting), T <sub>cal</sub> ± 5 °C [10]
3 A [11]	0 to ±500 mΩ	$\pm 500 \text{ m}\Omega$ to $\pm \text{infinity}$	

## **Overvoltage Protection**

Accuracy <sup>[12]</sup> (% of OVP limit + offset)	0.1% + 200 mV, typical
Temperature coefficient (% of OVP limit + offset)/°C	0.01% + 3 mV/°C , typical
Measurement location	Local sense
Maximum OVP limit value	210 V
Minimum OVP limit value	2 V

## **Pulsed Operation**

Dynamic load, minimum pulse cycle time <sup>[13]</sup>	100 µs/A

The following figure visually explains the terms used in the extended range pulsing sections.




Figure 6. Definition of Pulsing Terminology

## Extended Range Pulsing for PXIe-4137 (40W)<sup>[15]</sup>

The following figures illustrate the maximum pulse on time and duty cycle for the PXIe-4137 (40W) in a  $\geq$ 58 W cooling slot, for a desired pulse voltage and pulse current given zero bias voltage and current. The shaded areas allow for a quick approximation of output limitations and limiting parameters. Actual limits are described by equations in <u>Table 1</u>.





Figure 7. Pulse On-time vs Pulse Current and Pulse Voltage

Note Equations to solve for maximum pulse on time, t<sub>onMax</sub>, are shown in <u>Table 1</u>. Additionally, Equation 8 solves for pulse on time, t<sub>on</sub>, in terms of maximum pulse energy in <u>Example 1</u>: <u>Determining Extended Range Pulse</u> <u>On Time and Duty Cycle Parameters for the (40W)</u>.

#### Figure 8. Duty Cycle vs Pulse Current and Pulse Voltage



Note Equations to solve for maximum duty cycle, D<sub>Max</sub>, are shown in <u>Table 1</u>. Additionally, Equation 9 solves for pulse off time, t<sub>off</sub>, in terms of maximum pulse energy in <u>Example 1</u>: <u>Determining Extended Range Pulse</u> <u>On Time and Duty Cycle Parameters for the (40W)</u>.

Bias level limits	
Maximum voltage, V <sub>bias</sub>	200 V
Maximum current, I <sub>bias</sub>	1 A

#### Table 6. PXIe-4137 (40W) Pulse Level Limits

Specification	Value	Equation
Maximum voltage, V <sub>pulseMax</sub>	160 V	—

Specification		Value	Equation
Maximum current	, I <sub>pulseMax</sub>	3 A	-
Maximum on time, t <sub>onMax</sub> <sup>[16]</sup>	If I <sub>pulse</sub> > 1 A and ≥58 W Slot Cooling Capacity Chassis	Calculate using the equation or refer to <u>Figure 1</u> to estimate the value.	$t_{onMax} = 100 \text{ ms} * \frac{2 \text{ A}}{ I_{pulse}  - 1\text{ A}}$ , where $t_{onMax}$ is $\leq 167 \text{ s}$ (Equation 1)
	If I <sub>pulse</sub> > 1 A and <58 W Slot Cooling Capacity Chassis	Calculate using the equation.	$t_{onMax} = 10 \text{ ms}^* \frac{2 \text{ A}}{II_{pulse}I - 1\text{ A}}$ , where $t_{onMax}$ is $\leq 167 \text{ s}$ (Equation 2)
	If I <sub>pulse</sub> ≤ 1 A	t <sub>onMax</sub> = 167 s	-
Maximum pulse energy, E <sub>pulseMax</sub> <sup>[17]</sup>		0.4 J	$E_{pulse} =  V_{pulse} * I_{pulse} * t_{on} $ , where $E_{pulse} < E_{pulseMax}$ (Equation 3)
Maximum duty cycle, D <sub>Max</sub> <sup>[18]</sup>	If ≥58 W Slot Cooling Capacity Chassis	Calculate using the equation or refer to <u>Figure 2</u> to estimate the value.	$D_{Max} = \frac{(1.18 \text{ A})^2 - \text{II}_{bias}\text{I}^2}{\text{II}_{pulse}\text{I}^2 - \text{II}_{bias}\text{I}^2} * 100\%$ (Equation 4)
	If <58 W Slot Cooling Capacity Chassis	Calculate using the equation.	$D_{Max} = \frac{(1 \text{ A})^2 - II_{bias}I^2}{II_{pulse}I^2 - II_{bias}I^2} * 100\%$ (Equation 5)
Minimum pulse cycle time, t <sub>cycleMin</sub>		5 ms	$\label{eq:tcycle} \begin{split} t_{cycle} &= t_{on} + t_{off} \\ \text{, where } t_{cycle} > t_{cycleMin} \end{split}$

Specification		Value	Equation
			(Equation 6)
Maximum cycle average power,	≥58 W Slot Cooling Capacity Chassis	20 W	$P_{CA} = \frac{\left V_{pulse} * I_{pulse} * t_{on}\right  + \left V_{bias} * I_{bias} * t_{off}\right }{t_{on} + t_{off}}$
P <sub>CAMax</sub> <sup>[19]</sup>	<58 W Slot Cooling Capacity Chassis	10 W	$P_{CA} = \frac{t_{on} + t_{off}}{t_{on} + t_{off}}$ , where $P_{CA} < P_{CAMax}$
			(Equation 7)



**Note** Software will not allow settings that violate these limiting equations and will generate an error.

#### Related reference

- <u>Device Capabilities</u>
- <u>Device Capabilities</u>

## Extended Range Pulsing for PXIe-4137 (20W)<sup>[20]</sup>

Bias level limits	
Maximum voltage	200 V
Maximum current	1 A
Pulse level limits	
Maximum voltage	160 V
Maximum current	3 A
Maximum on time <sup>[21]</sup>	1 ms

Minimum pulse cycle time	5 ms
Energy	0.2 J
Maximum cycle average power	10 W
Maximum duty cycle	5%

#### Related reference

<u>Device Capabilities</u>

# Transient Response and Settling Time

Transient response	<70 μs to recover within 0.1% of voltage range after a load current change from 10% to 90% of range, device configured for fast transient response, typical	
Maximum slew rate <sup>[22],[23]</sup>	0.5A/µs	
Settling time <sup>[24]</sup>		
Voltage mode, 180 V step, unloaded <sup>[25]</sup>		<500 μs, typical
Voltage mode, 5 V step or smaller, unloaded <sup>[26]</sup>		<70 μs, typical
Current mode, full-scale step, 3 A to 100 μA ranges <sup>[27]</sup> <50 μs		<50 μs, typical
Current mode, full-scale step, 10 $\mu$ A range <sup>[27]</sup> <150 $\mu$ s,		<150 µs, typical
Current mode, full-scale step, 1 μA range <sup>[27]</sup> <300		<300 µs, typical

The following figures illustrate the effect of the transient response setting on the step response of the PXIe-4137 for different loads.






Figure 1.1 mA Range, No Load Step Response, Nominal





## Load Regulation

Voltage	
Device configured for local sense	200 mV per A of output load change (measured between output channel terminals) , typical
Device configured for remote sense	100 μV per A of output load change (measured between sense terminals) , typical

Current, device configured for local or remote	Load regulation effect included in current
sense	accuracy specifications, typical

#### Related reference

<u>Voltage</u>

# Measurement and Update Timing Characteristics

Available sample rates <sup>[28]</sup>		(1.8 MS/s)/ <b>N</b> where <b>N</b> = 1, 2, 3, 2 <sup>24</sup> , nominal	
Sample rate accuracy		Equal to PXIe_CLK100 accuracy, nominal	
Maximum measure rate to host		1.8 MS/s per channel, continuous, nominal	
Maximum source update	rate <sup>[29]</sup>	1	
Sequence mode	100,000	100,000 updates/s (10 μs/update), nominal	
Timed output mode	80,000 ι	80,000 updates/s (12.5 μs/update), nominal	
Input trigger to			
Source event delay		10 μs, nominal	
Source event jitter		1 μs, nominal	
Measure event jitter		1 μs, nominal	
Pulse mode timing and accuracy <sup>[30]</sup>			
Minimum pulse on time <sup>[3</sup>	1]		
PXIe-4137 (40W)[32]		10 μs, nominal	

PXIe-4137 (20W)	50 μs, nominal	
Minimum pulse off time [33]		50 μs, nominal
Pulse on time or off time programming resolution		100 ns, nominal
Pulse on time or off time programming accuracy		±5 μs, nominal
Pulse on time or off time jitter		1 μs, nominal

## **Remote Sense**

Voltage accuracy	Add 3 ppm of voltage range per volt of HI lead drop plus 1 $\mu$ V per volt of lead drop per ohm of corresponding sense lead resistance to voltage accuracy specifications
Maximum sense lead resistance	100 Ω
Maximum lead drop per lead	3 V, maximum 202 V between HI and LO terminals

**Note** Exceeding the maximum lead drop per lead value may cause the driver to report a sense lead error.

Related reference

Voltage

## Safety Interlock

The safety interlock feature is designed to prevent users from coming in contact with hazardous voltage generated by the SMU in systems that implement protective barriers with controlled user access points.

**Caution** Hazardous voltages of up to the maximum voltage of the PXIe-4137 may appear at the output terminals if the safety interlock terminal is closed. Open the safety interlock terminal when the output connections are accessible. With the safety interlock terminal open, the output voltage level/limit is limited to ±40 V DC, and protection will be triggered if the voltage measured between the device HI and LO terminals exceeds ±(42 V peak ±0.4 V).

Attention Des tensions dangereuses allant jusqu'à la tension maximale du PXIe-4137 peuvent apparaître aux terminaux de sortie si le terminal de verrouillage de sécurité est fermé. Ouvrez le terminal de verrouillage de sécurité lorsque les connexions de sortie sont accessibles. Lorsque le terminal de verrouillage de sécurité est ouvert, le niveau ou la limite de tension de sortie est limité à  $\pm$  40 V CC, et la protection se déclenchera si la tension mesurée entre les terminaux HI et LO de l'appareil dépasse  $\pm$  (42 Vpic  $\pm$  0,4 V).

**Caution** Do not apply voltage to the safety interlock connector inputs. The interlock connector is designed to accept passive, normally open contact closure connections only.

Attention N'appliquez pas de tension aux entrées du connecteur de verrouillage de sécurité. Le connecteur de verrouillage est conçu pour accepter uniquement des connexions à fermeture de contact passives, normalement ouvertes.

#### Safety interlock terminal open

Output	<±42.4 V peak
Setpoint	<±40 V DC
Safety interlo	ck terminal closed
Output	Maximum voltage of the device
Setpoint	Maximum selected voltage range

# Examples of Calculating Accuracy Specifications<sup>[34]</sup>

# Example 1: Calculating 5 °C Accuracy

Calculate the accuracy of 900 nA output in the 1  $\mu\text{A}$  range under the following conditions:

Ambient temperature	28 °C
Internal device temperature	within T <sub>cal</sub> ±5 °C[35]
Self-calibration	within the last 24 hours

Solution

Because the device internal temperature is within  $T_{cal} \pm 5$  °C and the ambient temperature is within 23 °C  $\pm 5$  °C, the appropriate accuracy specification is the following value:

0.03% + 100 pA

Calculate the accuracy using the following formula:

Accuracy = 900 nA \* 0.03 % + 100 pA = 270 pA + 100 pA = 370 pA Therefore, the actual output is within 370 pA of 900 nA.

# **Example 2: Calculating Remote Sense Accuracy**

Calculate the remote sense accuracy of 500 mV output in the 600 mV range. Assume the same conditions as in Example 1, with the following differences:

HI path lead drop	3 V
HI sense lead resistance	2 Ω
LO path lead drop	2.5 V
LO sense lead resistance	1.5 Ω

#### Solution

Because the device internal temperature is within T<sub>cal</sub> ±5 °C and the ambient temperature is within 23 °C ±5 °C, the appropriate accuracy specification is the following value:

0.02% + 50 μV

Because the device is using remote sense, use the following remote sense accuracy specification:

Add 3 ppm of voltage range per volt of HI lead drop plus 1  $\mu$ V per volt of lead drop per  $\Omega$  of corresponding sense lead resistance to voltage accuracy specifications.

Calculate the remote sense accuracy using the following formula:

Accuracy =  $(500 \text{ mV} * 0.02\% + 50 \mu\text{V}) + \frac{600 \text{ mV} * 3 \text{ ppm}}{1 \text{ Vof lead drop}} * 3 \text{V} + \frac{1 \mu\text{V}}{V^* \Omega} * 3 \text{V} * 2$   $\Omega + \frac{1 \mu\text{V}}{V^* \Omega} * 2.5 \text{ V} * 1.5\Omega$ =  $100\mu\text{V} + 50\mu\text{V} + 1.8\mu\text{V} * 3 + 6\mu\text{V} + 3.75 \mu\text{V}$ =  $165.15 \mu\text{V}$ Therefore, the actual output is within  $165.15 \mu\text{V}$  of 500 mV.

# Example 3: Calculating Accuracy with Temperature Coefficient

Calculate the accuracy of 900 nA output in the 1  $\mu$ A range. Assume the same conditions as in Example 1, with the following differences:

Ambient temperature	15 °C
---------------------	-------

Solution

Because the device internal temperature is within T<sub>cal</sub> ±5 °C, the appropriate accuracy specification is the following value:

0.03% + 100 pA

Because the ambient temperature falls outside of 23 °C ±5 °C, use the following temperature coefficient per °C outside the 23 °C ±5 °C range:

0.0006% + 4 pA

Calculate the accuracy using the following formula:

TemperatureVariation =  $(23 \degree C - 5 \degree C) - 15\degree C = 3\degree C$ 

Accuracy =  $(900 \text{ nA} * 0.03\% + 100 \text{ pA}) + \frac{900 \text{ nA} * 0.0006\% + 4 \text{ pA}}{1^{\circ}\text{C}} * 3^{\circ}\text{C}$ 

= 370 pA + 28.2 pA

= 398.2 pA

Therefore, the actual output is within 398.2 pA of 900 nA.

#### Examples of Determining Extended Range Pulse Parameters and Optimizing Slew Rate using NI SourceAdapt

**Note** Specifications listed in examples are for demonstration purposes only and do not necessarily reflect specifications for this device.

# Example 1: Determining Extended Range Pulse On Time and Duty Cycle Parameters for the PXIe-4137 (40W)

Determine the extended range pulsing parameters, assuming the following operating point.

Output function	Pulse Current
Pulse voltage limit, V <sub>pulse</sub>	80 V
Pulse current level, I <sub>pulse</sub>	3 A
Bias voltage limit, V <sub>bias</sub>	0.1 V
Bias current level, I <sub>bias</sub>	0 A
Pulse on time, t <sub>on</sub>	1.5 ms
Chassis' slot cooling capacity	≥58 W

Solution

Begin by calculating the pulse power using the following equation.

Pulse power = V<sub>pulse</sub> \* I<sub>pulse</sub> = 80 V \* 3 A = 240 W For PXIe-4137 (40W), refer to the following figures to identify next steps. First, verify the the region of operation using <u>Figure 1</u>, which shows 240 W is in the extended range pulsing region.

Next, refer to <u>Figure 1</u>, which shows the maximum pulse on time, t<sub>on</sub>, is limited by the maximum pulse energy, E<sub>pulseMax</sub>. Use the pulse energy equation **(Equation 3)** from <u>Table 1</u> to calculate the maximum pulse on time, t<sub>onMax</sub>(**Equation 8)**.

$$t_{onMax} = \left| \frac{E_{pulseMax}}{V_{pulse} * I_{pulse}} \right| \quad (Eq.8)$$
$$= \left| \frac{0.4 \text{ J}}{80 \text{ V}^* 3 \text{ A}} \right|$$
$$= 1.67 \text{ ms}$$

Next, refer to Figure 2, which shows the maximum duty cycle, D, is limited by the cycle average power,  $P_{CA}$ . If the required pulse on time is 1.5 ms and the module is installed in a chassis with slot cooling capacity  $\geq$ 58 W, use the cycle average power equation (Equation7) from Table 1 to calculate the minimum pulse off time,  $t_{offMin}$ (Equation 9).

$$t_{offMin} = \left| \frac{P_{CA} * t_{on} - V_{pulse} * I_{pulse} * t_{on}}{P_{CA} - V_{bias} * I_{bias}} \right| \quad (Eq.9)$$
  
=  $\left| \frac{20 \text{ W} * 1.5 \text{ ms} - 80 \text{ V} * 3 \text{ A} * 1.5 \text{ ms}}{20 \text{ W} - 0.1 \text{ V} * 0 \text{ A}} \right|$   
= 16.5 ms

Finally, verify that the pulse cycle time, t<sub>cycle</sub>, is greater than or equal to the minimum pulse cycle time, t<sub>cycleMin</sub> (5 ms). To calculate the pulse cycle time, use the following equation:

```
t_{cycle} = t_{on} + t_{off} (Eq. 6)
= 1.5 ms + 16.5 ms
=18 ms
```

In this case, the pulse cycle time meets the minimum pulse cycle time specification.

Therefore, a 80 V, 3 A pulse with an on time of 1.5 ms and a pulse off time of 16.5 ms is supported, since it fulfills the following criteria:

- Greater than the minimum pulse on time of 10 μs
- Equal to the minimum pulse off time of 16.5 ms to meet maximum cycle average power
- Greater than the minimum pulse cycle time of 5 ms

# Example 2: Determining Extended Range Pulse On Time and Duty Cycle Parameters for the PXIe-4137 (20W)

Determine the extended range pulsing parameters, assuming the following operating point.

Output function	Pulse Current
Pulse voltage limit, V <sub>pulse</sub>	80 V
Pulse current level, I <sub>pulse</sub>	3 A
Bias voltage limit, V <sub>bias</sub>	0.1 V
Bias current level, I <sub>bias</sub>	0 A
Pulse on time, t <sub>on</sub>	1.5 ms
Chassis' slot cooling capacity	≥58 W

#### Solution

Begin by calculating the pulse power using the following equation.

Pulse power = V<sub>pulse</sub> \* I<sub>pulse</sub> = 80 V \* 3 A =240 W

Since the pulse power of 240 W is within the 480 W region of <u>Figure 2</u>, the maximum configurable on time is 400 µs and maximum duty cycle is 2%.

For example, if the required pulse on time is 100  $\mu$ s, and the required pulse cycle time is 10 ms, calculate the pulse off time and verify the duty cycle using the following equations.

$$t_{off} = t_{cycle} - t_{on}$$
  
= 10 ms - 100µs  
= 9.9 ms  
Duty cycle =  $\frac{t_{on}}{t_{cycle}}$  \* 100%  
= 1 %

Therefore, a pulse with an on time of 100  $\mu$ s and 1% duty cycle would be supported, since it fulfills the following criteria:

- Greater than the minimum pulse on time of 50 μs
- Less than the maximum pulse on time of 400 μs and duty cycle of 2%
- Greater than the minimum pulse cycle time of 5 ms

# Example 3: Using NI SourceAdapt to Increase the Slew Rate of the Pulse

Determine the appropriate operating parameters and custom transient response settings, assuming the following example parameters.

Output function	Pulse Current
Pulse voltage limit, V <sub>pulse</sub>	160 V
Pulse current level, I <sub>pulse</sub>	3 A
Bias voltage limit, V <sub>bias</sub>	0.1 V
Bias current level, I <sub>bias</sub>	0 A
Transient response	Fast
Load, cable impedance	22.3 Ω, 1.8 μΗ
Pulse on time, t <sub>on</sub>	10 µs
Pulse off time, t <sub>off</sub>	4.99 ms

The SMU Transient Response can be configured to three predefined settings, Slow, Normal, and Fast. If these settings do not provide the desired pulse response, a fourth setting, Custom, enables NI SourceAdapt<sup>[36]</sup> technology which provides the ability to customize the SMU response to any load, and achieve an ideal response with minimum rise times and no overshoots or oscillations.





Figure 11. 10 µs Pulse Output with Load, Fast Transient Response

#### Solution

SourceAdapt allows users to set the desired gain bandwidth, compensation frequency, and pole-zero ratio through custom transient response to obtain the desired pulse waveform. To use SourceAdapt, first set the Transient Response to Custom.

To achieve the resulting waveform in the following figure, use the parameters in the following table.






Transient response	Custom
Current: Gain bandwidth	900 kHz
Current: Compensation frequency	200 kHz
Current: Pole-zero ratio	2

Gain bandwidth is directly proportional to the step response slew rate. The higher the gain bandwidth, the higher the slew rate. It is worth noting that increasing the gain bandwidth will likely increase ringing. However, this can likely be removed by appropriately setting the compensation frequency and the pole-zero ratio.

Figure 13. Example of Ringing Frequency



Compensation frequency and pole-zero ratio are used to determine the frequencies of the SMU control loop pole and zero, which can be used to optimize the system transient response by increasing phase margin and reducing ringing. To reduce the overshoot, it is recommended to set the compensation frequency close to the overshoot ringing frequency, see Fc in the figure above, and set the pole-zero ratio to be greater than 1.

For reference, the pole frequency and zero frequency are derived by the following equations.

Pole frequency = Compensation frequency \*  $\sqrt{Pole-zero ratio}$ 

Zero frequency =  $\frac{\text{Compensation frequency}}{\text{Pole-zero ratio}}$ 

These settings can be accessed through the Transient Response set to Custom: Voltage or Current.

## **Trigger Characteristics**

Input triggers		
Types Start, Source, Sequence Advance, Measure, Pulse		
Sources (PXI trigger lines <07>) [37]		
Polarity	Configurable	
Minimum pulse width	100 ns, nominal	
Destinations <sup>[38]</sup> (PXI trigger lines <07>)		
Polarity Active high (not configura	Active high (not configurable)	
Pulse width >200 ns, typical	>200 ns, typical	
Output triggers (events)		
Types Source Complete, Sequence Iteration Complete, Sequence Engine Done, Measure Complete, Pulse Complete, Ready for Pulse		
Destinations (PXI trigger lines <07>)		
Polarity Configurable		
Pulse width Configurable between 250 ns and 1.6 μs, nominal		

#### Protection

Automatic shutdown, output disconnect relay opens
Automatic shutdown, output disconnect relay opens
Automatic shutdown, output disconnect relay opens
Disable high voltage output, output disconnect relay opens

## Safety Voltages

DC voltage	±200 V	
Channel-to-earth	ground isolation	
Continuous	250 V DC, Measurement Category I	
Withstand	1000 V <sub>rms</sub> , verified by a 5 s withstand	

#### **Current Ratings**

DC current range	±1 A; ±3 A, pulse only

#### **Guard Output Characteristics**

Cable guard	
Output impedance	3 kΩ, nominal

1 year

1 mV, typical

#### Calibration Interval

Recommended calibration interval

#### Power Requirement

PXIe-4137 (40W)	3.0 A from the 3.3 V rail and 6.0 A from the 12 V rail
PXIe-4137 (20W)	2.5 A from the 3.3 V rail and 2.7 A from the 12 V rail

## Physical

Dimensions	3U, one-slot, PXI Express/CompactPCI Express module
	2.0 cm × 13.0 cm × 21.6 cm (0.8 in. × 5.1 in. × 8.5 in.)
Weight	
PXIe-4137 (20W)	419 g (14.8 oz)
PXIe-4137 (40W)	428 g (15.1 oz)
Front panel connectors	5.08 mm (8 position) combicon, 1 × 4.08 mm(3 position) combicon

### **Environmental Characteristics**

#### Temperature

Operating	0 °C to 55 °C
Storage	-40 °C to 71 °C
Humidity	
Operating	10% to 90%, noncondensing
Storage	5% to 95%, noncondensing
Pollution Degree	2
Maximum altitude	2,000 m (800 mbar) (at 25 °C ambient temperature)
Shock and Vibration	
Operating vibration	5 Hz to 500 Hz, 0.3 g RMS
Non-operating vibration	5 Hz to 500 Hz, 2.4 g RMS
Operating shock	30 g, half-sine, 11 ms pulse

#### **Environmental Standards**

This product meets the requirements of the following environmental standards for electrical equipment.

- IEC 60068-2-1 Cold
- IEC 60068-2-2 Dry heat
- IEC 60068-2-78 Damp heat (steady state)
- IEC 60068-2-64 Random operating vibration
- IEC 60068-2-6 Sinusoidal operating vibration
- IEC 60068-2-27 Operating shock

- MIL-PRF-28800F
  - Low temperature limits for operation Class 3, for storage Class 3
  - High temperature limits for operation Class 2, for storage Class 3
  - Random vibration for non-operating Class 3
  - Shock for operating Class 2

Note To verify marine approval certification for a product, refer to the product label or visit <u>ni.com/certification</u> and search for the certificate.

## Safety Compliance Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1

Note For safety certifications, refer to the product label or the <u>Product</u> <u>Certifications and Declarations</u> section.

#### **EMC Standards**

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions



**Note** In Europe, Australia, and New Zealand (per CISPR 11) Class A equipment is intended for use in non-residential locations.

**Note** Group 1 equipment is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



**Note** For EMC declarations, certifications, and additional information, refer to the Product Certifications and Declarations section.

#### **Environmental Management**

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the **Engineering a Healthy Planet** web page at <u>ni.com/environment</u>. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

#### EU and UK Customers

• A Waste Electrical and Electronic Equipment (WEEE)—At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit <u>ni.com/environment/weee</u>.

#### 电子信息产品污染控制管理办法(中国 RoHS)

• ◎ ● 中国 RoHS— NI 符合中国电子信息产品中限制使用某些有害物 质指令(RoHS)。关于 NI 中国 RoHS 合规性信息,请登录 ni.com/environment/ rohs\_china。(For information about China RoHS compliance, go to ni.com/ environment/rohs\_china.)

#### **Product Certifications and Declarations**

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit <u>ni.com/product-certifications</u>, search by model number, and click the appropriate link.

#### **NI Services**

Visit <u>ni.com/support</u> to find support resources including documentation, downloads, and troubleshooting and application development self-help such as tutorials and examples.

Visit <u>ni.com/services</u> to learn about NI service offerings such as calibration options, repair, and replacement.

Visit <u>ni.com/register</u> to register your NI product. Product registration facilitates technical support and ensures that you receive important information updates from NI.

NI corporate headquarters is located at 11500 N Mopac Expwy, Austin, TX, 78759-3504, USA.

<sup>1</sup> The ambient temperature of a PXI system is defined as the temperature at the chassis fan inlet (air intake).

<sup>2</sup> For increased capability, NI recommends installing the PXIe-4137 (40W) in a chassis with slot cooling capacity ≥58 W.

 $\frac{3}{2}$  Voltage levels and limits >|40 VDC| require the safety interlock input to be closed.

<sup>4</sup><sub>-</sub>Current is limited to 1 A DC. Higher levels are pulsing only.

<sup>5</sup> Power limit defined by voltage measured between HI and LO terminals.

<sup>6</sup> Accuracy is specified for no load output configurations. Refer to **Load Regulation** and **Remote Sense** sections for additional accuracy derating and conditions.

 $^{7}$  T<sub>cal</sub> is the internal device temperature recorded by the PXIe-4137 at the completion of the last self-calibration.

 $^{8}$  T<sub>cal</sub> is the internal device temperature recorded by the PXIe-4137 at the completion of the last self-calibration.

 $\frac{9}{2}$  3 A range above 1 A is for pulsing only.

 $\frac{10}{10}$  T<sub>cal</sub> is the internal device temperature recorded by the PXIe-4137 at the completion of the last self-calibration.

 $\frac{11}{2}$  3 A range above 1 A is for pulsing only.

 $\frac{12}{5}$  Overvoltage protection accuracy is valid with an ambient temperature of 23 °C ± 5 °C and with T<sub>cal</sub> ±5 °C. T<sub>cal</sub> is the internal device temperature recorded by the PXIe-4137 at the completion of the last self-calibration.

 $\frac{13}{13}$  For example, given a continuous pulsing load, if the largest dynamic step in current that the load sources/sinks is from 0.5 A to 1.0 A, then the maximum SMU current step is 0.5 A. Thus, the minimum dynamic load pulse cycle time is 50 µs. Minimum dynamic load pulse cycle time is independent of output voltage.<sup>[14]</sup>

 $\frac{14}{14}$  Measurable unit of  $\mu$ s/A is used because the minimum pulse cycle time is independent of output voltage

<sup>15</sup> Extended range pulses fall outside DC range limits for either current or power. Inrange pulses fall within DC range limits and are not subject to extended range pulsing limitations. Extended range pulsing is enabled by setting the Output Function to Pulse Voltage or Pulse Current.

 $\frac{16}{16}$  **Pulse on time** is measured from the start of the leading edge to the start of the trailing edge. See Figure 1.

 $\frac{17}{PXIe}$  Refer to Figure 1 to estimate the value and determine the limiting equation for a PXIe-4137 (40W) in a  $\geq$ 58 W Slot Cooling Capacity Chassis.

 $\frac{18}{18}$  Refer to Figure 2 to estimate the value and determine the limiting equation for a PXIe-4137 (40W) in a  $\geq$ 58 W Slot Cooling Capacity Chassis. If D $\geq$ 100%, consider switching Output Function from Pulse mode to DC mode.

 $\frac{19}{19}$  Refer to Figure 2 to estimate the value and determine the limiting equation for a PXIe-4137 (40W) in a ≥58 W Slot Cooling Capacity Chassis.

<sup>20</sup> Extended range pulses fall outside DC range limits for either current or power. Inrange pulses fall within DC range limits and are not subject to extended range pulsing limitations. Extended range pulsing is enabled by configuring the Output Function to Pulse Voltage or Pulse Current.

 $\frac{21}{1}$  **Pulse on time** is measured from the start of the leading edge to the start of the trailing edge. See <u>Figure 1</u>.

<sup>22</sup> Optimize transient response, overshoot, and slew rate with NI SourceAdapt by adjusting the Transient Response.

<sup>23</sup> To improve the slew rate, see <u>Examples of Determining Extended Range Pulse</u> <u>Parameters and Optimizing Slew Rate using NI SourceAdapt</u>.

 $\frac{24}{2}$  Measured as the time to settle to within 0.1% of step amplitude, device configured for fast transient response.

 $\frac{25}{2}$  Current limit set to  $\ge 60 \mu$ A and  $\ge 60\%$  of the selected current limit range.

 $\frac{26}{2}$  Current limit set to  $\geq 20 \ \mu$ A and  $\geq 20\%$  of selected current limit range.

 $\frac{27}{2}$  Voltage limit set to  $\geq 2$  V, resistive load set to 1 V/selected current range.

<sup>28</sup> When sourcing while measuring, both the Source Delay and Aperture Time affect the sampling rate. When taking a measure record, only the Aperture Time affects the sampling rate.

<sup>29</sup> As the source delay is adjusted or if advanced sequencing is used, maximum source rates vary. Timed output mode is enabled in Sequence Mode by setting Sequence Step Delta Time Enabled to True. Additional timing limitations apply when operating in pulse mode (Output Function is set to Pulse Voltage or Pulse Current).

<sup>30</sup> Pulse mode is enabled when the Output Function is set to Pulse Voltage or Pulse Current. This mode enables access to extended range pulsing capabilities. For PXIe-4137 (20W), shorter minimum on times for in-range pulses can be achieved using Sequence mode or Timed Output mode with the Output Function set to Voltage or Current.

 $\frac{31}{2}$  **Pulse on time** is measured from the start of the leading edge to the start of the trailing edge. See <u>Figure 6</u>.

<sup>32</sup> Optimize transient response, overshoot, and slew rate with NI SourceAdapt by adjusting the Transient Response.

 $\frac{33}{2}$  Pulses fall inside DC limits. **Pulse off time** is measured from the start of the trailing edge to the start of a subsequent leading edge.

<sup>34</sup> Specifications listed in examples are for demonstration purposes only and do not necessarily reflect specifications for this device.

 $\frac{35}{2}$  T<sub>cal</sub> is the internal device temperature recorded by the PXIe-4137 at the completion of the last self-calibration.

<sup>36</sup> Visit <u>ni.com</u> for more information about NI SourceAdapt Next-Generation SMU Technology.

<sup>37</sup> Pulse widths and logic levels are compliant with **PXI Express Hardware Specification Revision 1.0 ECN 1.** 

 $\frac{38}{2}$  Input triggers can be re-exported.