

Amplifier Built-in Ultra-compact Photoelectric Sensor





Ultra-compact Photoelectric Sensor Amplifier Built-in EX-20 SERIES Ver.2



Miniature-sized and still mountable with M3 screws

Miniaturization by using single chip optical IC

The beam-receiving photodiode and the A/D conversion circuit have been fabricated on a single chip optical IC (full custom). Hence, in spite of its miniature size, it has a performance and reliability which is equal to or better than the conventional product.



.....

Incorporates a sensitivity adjuster even in this size

The sensor incorporates a sensitivity adjuster in spite of its miniature size. It is convenient when you need fine adjustment. Further, the receiver of the thru-beam, side sensing type sensor incorporates an operation mode switch which can change the output operation.



BASIC PERFORMANCE

Long sensing range

The **EX-20** series achieves long distance sensing [thru-beam type: 2 m 6.562 ft, retroreflective type: 200 mm 7.874 in (when using the attached reflector), diffuse reflective type: 160 mm 6.299 in], despite its miniature size.

Hence, it is usable even on a wide conveyor.

Thru-beam type



Clear beam spot using red LED dot light source

The emission area of a dot light source is smaller than that of a conventional LED flat light source, and it is possible to design a high power, narrow beam. Since a red LED dot light source is used, the red beam spot is clear even at a far place, so that alignment and confirmation of sensing position is easy. Further, since the thru-beam type, too, incorporates a visible narrow beam, it can also reliably detect small parts, such as, chip components, lead frames, etc.





BASIC PERFORMANCE

Electric power saving*

The **EX-20** series achieves reductions in power consumption of up to 65 %. These sensors contribute to environmental friendliness.



ENVIRONMENTAL RESISTANCE

Waterproof IP67 (IEC)

The sensors features an IP67 rating to allow their use in process lines where water is used or splashed. Rust-resistant stainless steel sensor mounting brackets are available.

Note: If water splashes on the sensor during sensing operation, it may sense water as an object.

Incorporated an inverter countermeasure circuit*

The **EX-20** series become significantly stronger against inverter light and other extraneous light.

*Effective from production in April 2011.

MOUNTING

Identical size

Front sensing type of

thru-beam type and diffuse reflective type sensors have identical appearance. Moreover, since the mounting holes are symmetrical with respect to the beam axis center, the design becomes easy.

OPTIONS



Mounting section reinforced

It can be tightened with M3 screws. Moreover, metal inserts have been provided in the mounting holes so that the product is not damaged even in case of excess tightening.

Side sensing type

Front sensing type



Mounting spacer for front sensing type is available

Universal sensor mounting bracket **MS-EXL2-4** (for **EX-22/23/26/28/29**) and **MS-EX20-5** (for **EX-23** only) which can freely adjust the height and the angle of the sensor is available.

Universal sensor mounting bracket is available



Mounting of the front sensing type is possible from the rear side by using the mounting spacer.



Slit mask is available

 $\emptyset 0.5 \text{ mm } \emptyset 0.020 \text{ in round slit mask and } 0.5 \times 3 \text{ mm}$ $0.020 \times 0.118 \text{ in rectangular slit mask are available for both side sensing type and front sensing type sensors.$

FUNCTIONS

Bright 2-color indicator

A bright 2-color indicator has been incorporated in all types. (Orange LED: Operation indicator, Green LED: Stability indicator)

VARIETIES

Two types for suitable mounting

Two types, side sensing type and front sensing type sensors are available. Select depending on the place of mounting.

Side sensing type







(With sensitivity adjuster)

(Without sensitivity adjuster)

Туре			Appearance	Sensing range	Model No. (Note 3)	Output	Output operation	
		Front sensing			EX-21A	NPN open-collector transistor	Light-ON	
Thru-beam				1 m 3.281 ft	EX-21A-PN	PNP open-collector transistor		
	E		ĻĮ ĻĮ		EX-21B	NPN open-collector transistor		
	-068				EX-21B-PN	PNP open-collector transistor	Dark-ON	
		ensing		2 m 6.562 ft	EX-23	NPN open-collector transistor	Switchable either Light-ON or Dark-ON	
		Side s			EX-23-PN	PNP open-collector transistor		
9	2	Side sensing		30 to 200 mm 1.181 to 7.874 in (Note 1)	EX-29A	NPN open-collector transistor	Light-ON Dark-ON	
					EX-29A-PN	PNP open-collector transistor		
					EX-29B	NPN open-collector transistor		
ć	P L				EX-29B-PN	PNP open-collector transistor		
	uve	de sensing		5 to 160 mm 0.197 to 6.299 in (Note 2)	EX-22A	NPN open-collector transistor	Light-ON Dark-ON	
999	eller				EX-22A-PN	PNP open-collector transistor		
	- nage				EX-22B	NPN open-collector transistor		
8		Si	Ŭ		EX-22B-PN	PNP open-collector transistor		
	type	ont sensing		2 to 25 mm 0.079 to 0.984 in (Convergent point: 10 mm 0.394 in)	EX-24A	NPN open-collector transistor	- Light-ON	
ē	eam				EX-24A-PN	PNP open-collector transistor		
ectiv	sed t				EX-24B	NPN open-collector transistor	Ded. ON	
t refl	Diffu	Ľ			EX-24B-PN	PNP open-collector transistor	Dark-ON	
rgen	type	g		6 to 14 mm 0.236 to 0.551 in (Convergent point: 10 mm 0.394 in)	EX-26A	NPN open-collector transistor		
Conve	spot beam	de sensir			EX-26A-PN	PNP open-collector transistor	Light-ON	
					EX-26B	NPN open-collector transistor		
	Smal	Ñ			EX-26B-PN	PNP open-collector transistor	Dark-ON	
v reflective	n type	Side sensing		45 to 115 mm 1.772 to 4.528 in	EX-28A	NPN open-collector transistor		
	spot bea				EX-28A-PN	PNP open-collector transistor	Light-ON	
w-vie/	stances				EX-28B	NPN open-collector transistor		
Narrov	Long di				EX-28B-PN	PNP open-collector transistor	Dark-ON	

ORDER GUIDE

NOTE: Mounting bracket is not supplied with the sensor. Please select from the range of optional sensor mounting brackets (four types) or universal sensor mounting bracket. (Refer to p.6)

Notes: 1) The sensing range of the retroreflective type sensor is specified for the **RF-200** reflector. Further, the sensing range is the possible setting range for the reflector. The sensor can detect an object less than 30 mm 1.181 in away.

However, if the reflector is set 100 mm 3.937 in or less away, the sensing object should be opaque.

 In case of using this product at a sensing range of 50 mm 1.969 in or less, take care that the sensitivity adjustment range becomes extremely narrow.

3) The model No. with "**P**" shown on the label affixed to the thru-beam type sensor is the emitter, "**D**" shown on the label is the receiver.



ORDER GUIDE

Package without reflector

Retroreflective type is also available without the reflector **RF-200**. When ordering this type, suffix "-**Y**" to the model No. (e.g.) Without reflector type of **EX-29A-PN** is "**EX-29A-PN-Y**".

5 m 16.404 ft cable length type

5 m 16.404 ft cable length type (standard: 2 m 6.562 ft) is also available for NPN output type (including package without reflector of retroreflective type sensor). When ordering this type, suffix "-C5" to the model No. (e.g.) 5 m 16.404 ft cable length type of EX-29A-Y is "EX-29A-Y-C5".

Accessory

• RF-200 (Reflector)



OPTIONS

Designatio	n	Model No.	Description			
e	ensing type	OS-EX20-05	Slit on one side • Sensing range: 200 mm 7.874 in • Min. sensing object: ø2.6 mm ø0.102 in			
nask eam typ y	For front se	(0.020 in	 Slit on both sides Sensing range: 40 mm 1.575 in Min. sensing object: Ø0.5 mm Ø0.020 in 			
nd slit r - thru-be isor onl	For side sensing type	OS-EX20E-05 (Slit size ø0.5 mm 0.020 in	Slit on one side • Sensing range: 350 mm 13.780 in • Min. sensing object: ø3 mm ø0.118 in			
Rou (For ser			Slit on both sides • Sensing range: 70 mm 2.756 in • Min. sensing object: ø0.5mm ø0.020 in			
ask e	ensing type	OS-EX20-05×3	Slit on one side • Sensing range: 600 mm 23.622 in • Min. sensing object: ø2.6 mm ø0.102 in			
r slit me eam typ ly	For front se	$\left(\begin{array}{c} \sin \sin \sin 2 \theta \ 0.5 \times 5 \ \text{mm} \\ 0.020 \times 0.118 \ \text{in} \end{array}\right)$	Slit on both sides • Sensing range: 300 mm 11.811 in • Min. sensing object: 0.5 × 3 mm 0.020 × 0.118 in			
tangula · thru-bé nsor on	ensing type	OS-EX20E-05×3 (Slit size 0.5 × 3 mm) 0.020 × 0.118 in	Slit on one side • Sensing range: 800 mm 31.496 in • Min. sensing object: ø3 mm ø0.118 in			
Rec (Foi	For side se		Slit on both sides • Sensing range: 400 mm 15.748 in • Min. sensing object: 0.5 × 3 mm 0.020 × 0.118 in			
Reflector For retroreflectiv type sensor only	/e)	RF-210	 Sensing range: 50 to 400 mm 1.969 Min. sensing object: ø30 mm ø1.181 	to 15.748 in in		
Reflector mounting bracket		MS-RF21-1	Protective mounting bracket for RF-210 It protects the reflector from damage an	d maintains alignment.		
Reflective tape (For retroreflective (type sensor only)		RF-11	 Ambient temperature: -25 to +50 °C -13 to +122 °F Ambient humidity: 35 to 85 % RH Notes Keen the tane free from stress. If it is 			
		RF-12	 Pressed too much, its capability may deteriorate. Do not cut the tape. It will deteriorate the sensing performance. Sensing range: 60 to 280 mm 2.362 to 11.024 in 			

Round slit mask

Fitted on the front face of the sensor with one-touch.

• OS-EX20-05 • OS-EX20E-05



Rectangular slit mask

Fitted on the front face of the sensor with one-touch.

• OS-EX20-05×3 • OS-EX20E-05×3





Reflector mounting bracket

Reflector

• MS-RF21-1



Reflective tape

1.181 in -

0.7 mm 30 mm 0.028 in

• RF-11

8 mm × 0.315 in l

Two M3 (length 12 mm 0.472 in) screws with washers are attached.





OPTIONS

Designation Model No.			Description			
	MS-EX20-1	Back angled mounting bracket for front sensing type sensor (The thru-beam type sensor needs two brackets.)				
Sensor mounting	MS-EX20-2	Foot angled mounting bracket for side sensing type sensor (The thru-beam type sensor needs two brackets.)				
bracket	MS-EX20-3	L-shaped mounting bracket for front sensing type sensor (The thru-beam type sensor needs two brackets.)				
	MS-EX20-4	Back angled mounting bracket for side sensing type sensor (The thru-beam type sensor needs two brackets.)				
Universal sensor	MS-EXL2-4	For EX-22¤/23¤/26¤/ EX-28¤/29¤	It can adjust the height and the angle of the sensor.			
(Note 1)	MS-EX20-5	For EX-23 □ only	(The thru-beam type sensor needs two brackets.)			
Mounting spacer (For front sensing type sensor only)	MS-EX20-FS	It is used when mounting the front sensing type from the rear side. (One set consists of 10 pcs.)				
Sensor checker CHX-SC2		It is useful for beam alignment of thru-beam type sensors. The optimum receiver position is given by indicators, as well as an audio signal				

Notes: 1) Note that the axis position of EX-23 is different when replacing the mounting bracket MS-EX20-5

Material: LJ Stainless steel (SUS304) Material: Stainless steel (SUS304) Two M3 (length 5 mm 0.197 in) pan head screws [stainless steel (SUS304)] are attached.

Ø

Two M3 (length 14 mm 0.551 in) screws with washers [stainless steel (SUS304)] are attached.

with MS-EXL2-4.

Sensor checker **Mounting spacer** Universal sensor mounting bracket • CHX-SC2 • MS-EX20-FS • MS-EXL2-4 • MS-EX20-5 One set consists of 10 pcs. Fine P adjustment +3S 360° rotation 360° rotation Material: Die-cast zinc alloy Sensor checker Height adjustment: 15 mm 0.591 in Two M3 (length 12 mm 0.472 in) screws with washers [stainless Height adjustment: MS-EX20-FS 15 mm 0.591 in steel (SUS)], one M3 (length 10 mm 0.394 in) hexagon-socket Two M3 (length 14 mm 0.551 in) screws with washers, one M3 (length 00 head bolt [stainless steel (SUS)], and one M3 hexagon nut [stainless 10 mm 0.394 in) hexagon-socket head bolt [stainless steel (SUS)], and steel (SUS)] are attached. one M3 hexagon nut [stainless steel (SUS)] are attached.

Sensor mounting bracket





Stainless steel (SUS304) Two M3 (length 5 mm 0.197 in)

pan head screws [stainless

steel (SUS304)] are attached. • MS-EX20-3



6

Material: Die-cast zinc alloy

Material: Stainless steel (SUS304) Two M3 (length 14 mm 0.551 in) screws with washers [stainless steel (SUS304)] are attached.

• MS-EX20-4



Material: Nylon 6



SPECIFICATIONS

Туре		Thru-beam		Retroreflective	Diffuse reflective	Convergent reflective Narrow-view reflective			
						Diffused beam type	Small spot beam type	Long distance spot beam type	
		Front sensing	Side sensing	Side sensing	Side sensing	Front sensing	Side sensing	Side sensing	
	Model No. Light-ON	EX-21A(-PN)	EX-23(-PN)	EX-29A(-PN)	EX-22A(-PN)	EX-24A(-PN)	EX-26A(-PN)	EX-28A(-PN)	
Item	(Note 2) Dark-ON	EX-21B(-PN)	(Note 3)	EX-29B(-PN)	EX-22B(-PN)	EX-24B(-PN)	EX-26B(-PN)	EX-28B(-PN)	
CE r	narking directive compliance			EMC	Directive, RoHS Di	rective	1		
Sen	sing range	1 m 3.281 ft	2 m 6.562 ft	30 to 200 mm 1.181 to 7.874 in (Note 4)	5 to 160 mm 0.197 to 6.299 in (Note 5) with white non-glossy paper (200 × 200 mm) (7.874 × 7.874 in)	2 to 25 mm 0.079 to 0.984 in (Conv. point: 10 mm 0.394 in) with white non-glossy paper (50 × 50 mm) (1.969 × 1.969 in)	6 to 14 mm 0.236 to 0.551 in (Conv. point: 10 mm 0.394 in) with white non-glossy paper (50 × 50 mm 1.989 × 1.969 in), spot diameter of mm 0.039 in with setting distance 10 mm 0.0394 in	45 to 115 mm 1.772 to 4.528 in with white non-glossy paper (100 \times 100 mm 3.937 \times 3.937 in), spot diameter ø5 mm ø0.197 in with setting distance 80 mm 3.150 in	
Sensing object		Min. ø2.6 mm ø0.102 in opaque object (Setting distance between emitter and receiver: 1 m 3.281 ft	Min. ø3 mm ø0.118 in opaque object (Setting distance between emitter and receiver: 2 m 6.562 ft)	ø15 mm ø0.591 in or more opaque or tran slucent object (Note 4, 6)	Opaque, translucent or transparent object (Note 6)	$\begin{array}{l} \text{Min. } \emptyset 0.1 \text{ mm} \\ \emptyset 0.004 \text{ in} \\ \text{copper wire} \\ \left(\begin{array}{c} \text{Setting distance:} \\ 10 \text{ mm } 0.394 \text{ in} \end{array} \right) \end{array}$	$\begin{array}{l} \text{Min. } \emptyset 0.1 \text{ mm} \\ \emptyset 0.004 \text{ in} \\ \text{copper wire} \\ \left(\begin{array}{c} \text{Setting distance:} \\ 10 \text{ mm } 0.394 \text{ in} \end{array} \right) \end{array}$	Opaque, translucent or transparent object (Note 6) (Min. ø1 mm ø0.039 in copper wire at setting distance 80 mm 3.150 in)	
Hys	eresis		15 % or less of operation distance [50 × 50 mm 1.969 × 1.969 in (EX-22 □: 200 × 200 mm 7.874 × 7.874 in, EX-28 □: 100 × 100 mm 3.937 × 3.937 in) (with white non-glossy paper)]						
Rep (per	eatability pendicular to sensing axis)	0.05 mm 0.0	002 in or less	0.5 mm 0.020 in or less	0.3 mm 0.012 in or less	0.1 mm 0.004 in or less (Setting distance: 10 mm 0.394 in)	0.05 mm 0.002 in or less (Setting distance: 10 mm 0.394 in)	0.3 mm 0.012 in or less	
Sup	ply voltage			12 to 24 V DC	±10 % Ripple P-	P 10 % or less			
Curr	ent consumption	Emitter: 10 mA or less,	Emitter: 10 mA or less, Receiver: 10 mA or less 13 mA or less 15 mA or less						
Out	but	<npn output="" type=""> NPN open-collector transistor Maximum sink current: 50 mA Applied voltage: 30 V DC or less (between output and 0 V) Residual voltage: 2 V or less (at 50 mA sink current) 1 V or less (at 16 mA sink current) PNP output type> PNP open-collector transistor Maximum source current: 50 mA Applied voltage: 30 V DC or less (between output and +V) Residual voltage: 2 V or less (at 16 mA sink current) 1 V or less (at 16 mA sink current) </npn>							
	Utilization category				DC-12 or DC-13				
	Short-circuit protection				Incorporated				
Response time		0.5 ms or less							
Ope	ration indicator	Orange LED (lights up when the output is ON) (thru-beam type: located on the receiver)							
Stat	ility indicator	Green LED (lights up under stable light received condition or stable dark condition), located on the receiver Green LED (lights up under stable light received condition or stable dark condition)							
Sen	sitivity adjuster		Continuously variable adjuster, located on the emitter	^{r,} Continuously variable adjuster Continuously variable adjuster				ariable adjuster	
Ope	ration mode switch		Located on the receiver						
	Pollution degree	3 (Industrial environment)							
JCe	Protection				IP67 (IEC)				
istar	Ambient temperature	-25 to +55 °C -13 to +131 °F (No dew condensation or icing allowed), Storage: -30 to +70 °C -22 to +158 °F						+158 °F	
l res	Ambient humidity	35 to 85 % RH, Storage: 35 to 85 % RH							
enta	Ambient illuminance	Incandescent light: 3,000 & or less at the light-receiving face							
Dume	Voltage withstandability	1,000 V AC for one min. between all supply terminals connected together and enclosure							
nvird	Insulation resistance	20 MΩ, or more, with 250 V DC megger between all supply terminals connected together and enclosure							
ш	Vibration resistance	10 to 500 Hz frequency, 3 mm 0.118 in double amplitude (20 G max.) in X, Y and Z directions for two hours each							
	Shock resistance	500 m/s ² acceleration (50 G approx.) in X, Y and Z directions three times each							
Emi	ting element	Red LED (modulated)							
	Peak emission wavelength	640 nm 0.025 mil 650 nm 0.026 mil 680 nm 0.027 mil 680 nm 0.027 mil 680 nm 0.027 mil 680 nm 0.027 mil 650 nm 0.026 mil 650 nm 0.026 mil							
Mate	erial	Enclosure: Polyarylate, Lens: Polyarylate							
Cab	le	0.1 mm ² 3-core (thru-beam type sensor emitter: 2-core) cabtyre cable, 2 m 6.562 ft long							
Cable extension		Extension up to total 50 m 164.042 ft is possible with 0.3 mm ² , or more, cable (thru-beam type: both emitter and receiver).							
Wei	ght	Net weight (each emitter and receiver): 20 g approx. Second s							
Acc	essories		Adjusting screwdriver: 1 pc.	RF-200 (Reflector): 1 pc. Adjusting screwdriver: 1 pc.	Adjusting screwdriver: 1 pc.		Adjusting scre	ewdriver: 1 pc.	
Note	 s: 1) where measurement (a mbient temperature of 2) Model Nos. having the 3) Either Light-ON or Dark-(4) The sensing range and RF-200 reflector. Furth sensor can detect an (100 mm 3.937 in or let 5) In case of using this pisensitivity adjustment 6) Make sure to confirm (a mbient sensor (a sensitivity)) and (a sensitivity) adjustment (b) Make sure to confirm (a sensitivity)). 	conditions have not of +23 °C +73.4 °F. suffix "- P N" are Pt DN can be selected b d the sensing object her, the sensing rar object less than 30 ss away, the sensir orduct at a sensing range becomes ext detection with an action	veen specified pre- NP output type. y the operation mode to of the retroreflect age is the possible mm 1.181 in away ng object should be range of 50 mm 1 tremely narrow. ctual sensor before	ecisely, the condition e switch (located on the tive type sensor and setting range for th . However, if the re- e opaque. .969 in or less, take e use.	ons used were an he receiver). e specified for the he reflector. The flector is set e care that the	Reflector cannot be placed in this range	Actual sensing rai of the sensor 30 mm 1.181 in Setting rang of the reflector	nge 200 mm 7.874 in je tor Reflector	

I/O CIRCUIT AND WIRING DIAGRAMS

NPN output type



SENSING CHARACTERISTICS (TYPICAL)

EX-21 EX-23 EX-29 EX-22



EX-21

Parallel deviation





Angular deviation

Parallel deviation with round slit masks (ø0.5 mm ø0.020 in)





Parallel deviation with rectangular slit

Thru-beam type



SENSING CHARACTERISTICS (TYPICAL)

EX-23





Thru-beam type Parallel deviation with round Parallel deviation with rectangular slit slit masks (ø0.5 mm ø0.020 in) masks (0.5 × 3 mm 0.020 × 0.118 in) 400 Slit on one side . E 300 E 11.811 늘 Slit on one side E Setting distance L distance L 7.874 7.874 Emitter Slit on both sides 0.5 Setting 3.937 - 8-Slit on both sides Receiver 0 40 1.575 0+ 20 10 0.394 10 0.394 20 0.787

20

0.787

Ò Left ← Center → Righ Operating point ℓ (mm in) Right

0.787

Retroreflective type

Diffuse reflective type

Ó

Left ← Center → Righ Operating point ℓ (mm in)

Emitte

40 1.575

- f -

Receiver

20 0.787

+ Right

EX-29□

Parallel deviation



Angular deviation



EX-22□

Sensing field

Correlation between sensing object size and sensing range

200 Gray non-glossy paper Lightness: 6 150 White nonglossy pape 200 × 200 mm 100 Non-glossy pape 50 · P enso 0. 2 2 0.079 0.157 0 079 0.157 Center Left 🗲 - Right Operating point { (mm in)

EX-24□

Sensing fields



0

50

200 7.874

a × a mm a × a in White non-glossy

150

-----Sensor

2 0.079

- Right

4 0.157

paper

ŕ Sensor

100

White non-glossy paper

side length a (mm in)

As the sensing object size becomes smaller than the standard size (white non-glossy paper 200 × 200 mm 7.874×7.874 in), the sensing range shortens, as shown in the left graph.

Convergent reflective type

SENSING CHARACTERISTICS (TYPICAL)

EX-24□

Correlation between lightness and sensing range



The sensing region (typical) is represented by oblique lines in the left figure. However, the sensitivity should be set with enough margin because of slight variation in products.

Lightness shown on the left may differ slightly from the actual object condition.

EX-26□

Sensing fields



· Vertical (up and down) direction



Correlation between lightness and sensing range



The sensing region (typical) is represented by oblique lines in the left figure. However, the sensitivity should be set with enough margin because of slight variation in products. The graph is drawn for the

maximum sensitivity setting.

Lightness shown on the left may differ slightly from the actual object condition.

Correlation between material (50 × 50 mm 1.969 × 1.969 in) and sensing range



The bars in the graph indicate the sensing range (typical) for the respective material. However, there is a slight variation in the sensing range depending on the product. Further, if there is a reflective object (conveyor, etc.) in the background of the sensing object, since it affects the sensing, separate it by more than twice the sensing range shown in the left graph, or adjust the sensitivity adjuster.

The graph is drawn for the maximum sensitivity setting.

Narrow-view reflective type



EX-28□





As the sensing object size becomes smaller than the standard size (white non-glossy paper 100 × 100 mm 3.937×3.937 in), the sensing range shortens, as shown in the left graph.

Convergent reflective type

Correlation between material (50 × 50 mm 1.969 × 1.969 in) and sensing range



The bars in the graph indicate the sensing range (typical) for the respective material. However, there is a slight variation in the sensing range depending on the product. Further, if there is a reflective object (conveyor, etc.) in the background of the sensing object, since it affects the sensing, separate it by more than twice the sensing range shown in the left graph.

Convergent reflective type

PRECAUTIONS FOR PROPER USE

 Never use this product as a sensing device for personnel protection.

 In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection

applicable in each region or country.

Mounting

- Mount using M3 screws. The tightening torque should be 0.5 $N{\cdot}m$ or less.



Side sensing



M3 screws

M3 pan head screws (Note)

Note: When mounting the front sensing type sensor, use M3 pan head screws without washers, etc.

• When mounting the front sensing type from the backside, fit the mounting spacer (MS-EX20-FS) and fix with screws.

Mounting method

① Fit the mounting spacer on the sensor.



② Align the mounting holes of the mounting spacer and the sensor and mount with M3 screws. The tightening torque should be 0.5 N·m or less.



Sensitivity adjustment (side sensing type only)

Step	Sensitivity adjuster	Description
1	MAX	Turn the sensitivity adjuster fully counterclockwise to the minimum sensitivity position (• mark).
2	A	In the light received condition, turn the sensitivity adjuster slowly clockwise and confirm the point (A) where the sensor enters the "Light" state operation.
3	B MAX	In the dark condition, turn the sensitivity adjuster further clockwise until the sensor enters the "Light" state operation and then bring it back to confirm point (B) where the sensor just returns to the "Dark" state operation. (If the sensor does not enter the "Light" state operation even when the sensitivity adjuster is turned fully clockwise, this extreme position is point (B).
4	Optimum position B B B B B B B B B B B B B	The position at the middle of points (A) and (B) is the optimum sensing position.

Notes: 1) Use the attached adjusting screwdriver to turn the adjuster slowly. Turning with excessive strength will damage the adjuster.

2) In case of using EX-22 at a sensing distance of 50 mm 1.969 in or less, take care that the sensitivity adjustment range becomes extremely narrow.

Operation mode switch (EX-23 only)

Switch position	Description
Ŕ	Light-ON mode is obtained when the operation mode switch (located on the receiver) is turned fully clockwise (L side).
	Dark-ON mode is obtained when the operation mode switch (located on the receiver) is turned fully counterclockwise (D side).

Note: Operation mode switch should be turned fully till it stops.

Stability indicator

 The stability indicator (green) lights up when the incident light intensity has sufficient margin with respect to the operation level.

If the incident light intensity level is such that the stability indicator lights up, stable sensing can be done without the light received operation and the light interrupted operation being affected by a change in ambient temperature or supply voltage.



Glossy object sensing (EX-29)

• Please take care of the following points when detecting materials having a gloss.



Wiring

• Excess bending of the cable or stress applied to the cable may disconnect the internal lead wire.

Others

- Do not use during the initial transient time (50 ms) after the power supply is switched on.
- If sensors are mounted close together and the ambient temperature is near the maximum rated value, provide for enough heat radiation / ventilation.
- If a reflective object is present in the background, the sensing of EX-28 may be affected. When setting the sensor, make sure to confirm that the reflective object has no effect. In case the reflective object affects the sensing, take measures such as removing the reflective object or coloring it in black, etc.



EX-23 Operation indicator (Orange) (Note 1) Operation mode switch (Note 2) Stability indicator (Green) (Note 1) 10.5 8.2 0.323 2.8 3 (Nu1 \oplus Beam axis 9.5 0.374 ŧ 13 19 Ø ((\$ 2 0.748 0 6.5 0.256 Ŧ 3 0 0 2-ø3.2 ø0.126 mounting holes ø2.5 ø0.098 cable 2 m 6.562 ft long cable, 3.5

Notes: 1) Not incorporated on the emitter. 2) It is the sensitivity adjuster on the emitter.

EX-29: EX-22: EX-26: EX-28:



RF-200 Reflector (Accessory for the retroreflective type sensor)



Material: Acrylic (Reflector) ABS (Base)





Sensor

Reflector (Optional)



Material: Acrylic (Reflector) ABS (Base) Two M3 (length 8 mm 0.315 in) screws with washers and two nuts are attached.





Two M3 (length 12 mm 0.472 in) screws with washers are attached.

Material: Stainless steel (SUS304)

13_ 0.512

MS-EX20-1



.984

12.5 <mark>0.49</mark>2

ŧ t 1.2 t 0.047

25

Material: Stainless steel (SUS304)

Two M3 (length 5 mm 0.197 in) pan head screws [stainless steel (SUS304)] are attached.

Sensor mounting bracket (Optional)

Assembly dimensions

Mounting drawing with EX-21



MS-EX20-2



MS-EX20-3



Material: Stainless steel (SUS304) Two M3 (length 5 mm 0.197 in) pan head screws [stainless steel (SUS304)] are attached.

Sensor mounting bracket (Optional)

Assembly dimensions

Mounting drawing with the receiver of EX-23 -



Assembly dimensions

Mounting drawing with the receiver of EX-21



Sensor mounting bracket (Optional)

Assembly dimensions

Mounting drawing with the receiver of EX-23 -



MS-EX20-4

1





Material: Stainless steel (SUS304) Two M3 (length 14 mm 0.551 in) screws with washers [stainless steel (SUS304)] are attached.



Material: Nylon 6

Two M3 (length 12 mm 0.472 in) screws with washers [stainless steel (SUS)], one M3 (length 10 mm 0.394 in) hexagon sockethead bolt [stainless steel (SUS)], and one M3 hexagon nut [stainless steel (SUS)] are attached.





Assembly dimensions

Mounting drawing with the receiver of EX-21

0.2

14



8.5

19.5-

Mounting spacer (Optional)

0.335

Note: This is the adjustable range of the movable part.

Material: Die-cast zinc alloy

Disclaimer

The applications described in the catalog are all intended for examples only. The purchase of our products described in the catalog shall not be regarded as granting of a license to use our products in the described applications. We do NOT warrant that we have obtained some intellectual properties, such as patent rights, with respect to such applications, or that the described applications may not infringe any intellectual property rights, such as patent rights, of a third party.



Panasonic Industry Co., Ltd.

Industrial Device Business Division 7-1-1, Morofuku, Daito-shi, Osaka 574-0044, Japan industrial.panasonic.com/ac/e/