

Positronic Provides Complete Capability Mission Statement

Experience

- Founded in 1966
- Involvement in the development of international connector specifications through EIA®, IEC and ISO as well as PICMG®.
- Introduction of new and unique connector products to the electronics industry.
- Patent holder for many unique connector features and manufacturing techniques.
- Vertically integrated manufacturing raw materials to finished connectors.

Technology

- Expertise with solid machined contacts provides a variety of high reliability connectors including high current density power connectors.
- Quality Assurance lab is capable of testing to IEC, EIA, UL, CUL, military and customer-specified requirements.
- In-house design and development of connectors based on market need or individual customer requirements.
- Internal manufacturing capabilities include automatic precision contact machining. injection molding, stamping, plating operations and connector assembly.
- Manufacturing locations in southwest Missouri, U.S.A. (headquarters); Puerto Rico, France, China, Singapore, and India. Total square footage: 407,441.

Support

- Quality Systems: Select locations qualified to ISO 9001, ISO 14001, AS9100, MIL-STD-790 and customer "dock to stock" programs. Applicable products qualified to MIL-DTL-24308, AS39029, DSCC 85039, MIL-DTL-28748, Space D32, GSFC S-311-P-4 and GSFC S-311-P-10.
- Compliance to a variety of international and customer specific environmental requirements.
- Large in-house inventory of finished connectors. Customer specific stocking programs.
- Factory direct technical sales support in major cities worldwide.
- One-on-one customer support from worldwide factory locations.
- World class web site.
- Value-added solutions and willingness to develop custom products with reasonable price and delivery.

Regional Headquarters



Auch, France



"To utilize product flexibility and application

assistance to present quality interconnect solutions which represent value to customers worldwide."



Products described within this catalog may be protected by one or more of the following US patents:

#4,900,261[†] #5,255,580 #5,329,697 #6,260,268 #6,835,079 #7,115,002

[†]Patented in Canada, 1992 Other Patents Pending

Positronic Industries' FEDERAL SUPPLY CODE (Cage Code) FOR MANUFACTURERS is 28198

Unless otherwise specified, dimensional tolerances are:

- ±0.001 inches [0.03 mm] for male contact mating diameters.
- ±0.003 inches [0.08 mm] for contact termination diameters.
- ±0.005 inches [0.13 mm] for all other diameters. 3)
- ±0.015 inches [0.38 mm] for all other dimensions.

POSITRONIC® IS AN ITAR REGISTERED COMPANY

Information in this catalog is proprietary to Positronic and its subsidiaries. Positronic believes the data contained herein to be reliable. Since the technical information is given free of charge, the user employs such information at his own discretion and risk. Positronic Industries assumes no responsibility for results obtained or damages incurred from use of such information in whole or in part.

CONNECTOR DESCRIPTIONS



COMBINATION D-SUBMINIATURE STANDARD AND HIGH DENSITY

CB series connectors are available in standard density versions, which have fixed size 20 signal contacts and size 8 power, shielded, high voltage and air contacts. High density CB series connectors offer fixed size 22 signal contacts, size 8 contacts or size 16 power contacts. These connectors are available in various performance levels for best cost/performance ratio. Thermocouple contact options are also available.




COMBINATION D-SUBMINIATURE CRIMP CONTACTS STANDARD AND HIGH DENSITY

CBC series connectors offer crimp removable contacts for signal, power, shielded, high voltage and air contacts applications. These connectors are available in standard and high density versions. Thermocouple contact options are also available.



COMBINATION CONTACT DUAL PORT CONNECTORS

CBDP series. Offers seventeen different combinations of power and signal contact stacked assemblies. Size 20 signal contacts and size 8 power contacts.



COMBO-D CONNECTOR SAVERS - ACBDP and ACBMP SERIES

ACBDP and ACBMP series. Combo-D connector savers with size 20 and size 8 contacts. Available for all standard Combo-D variants in shell sizes 1 through 6.

TABLE OF CONTENTS



G E N E R A L I N F O R M A T I O N

CBD/CBM SERIES	
CBD/CBM Series Introduction	3
Technical Characteristics	4 5
Contact Variants	5 6
Code 2 Solder Cup Connector and Code 3, 35, 36 and 37 Straight Printed Board Mount Connector	7
Code 5, 55 and 57 Straight Angle (90°) Printed Board Mount Connector	8
Code 5, 55 and 57 Shell Size 6 - Right Angle (90°) Printed Board Mount Connector	9
Code 7, 75 and 77 Metric System Right Angle (90°) Printed Board Mount Connector	10
Right Angle (90°) and Straight Printed Contact Hole Pattern with	
0.078 [1.98] ø, 0.094 [2.39] ø and 0.125 [3.18] ø Power Contacts	11-12
Right Angle (90°) Printed Board Contact Hole Pattern with 0.125 [3.18] ø Power Contacts	13-14
Code 85 Right Angle (90°) Printed Board Mount Connector with FDS4201D or MDS4201D Shielded Contacts	15
Straight Printed Board Mount Contact Hole Pattern with	
FDS4201D and MDS4201D Shielded Contacts	16-17
Right Angle (90°) Printed Board Mount Contact Hole Pattern with	
FRT4201D and MRT4201D Shielded Contacts	18-19
Code 93 Compliant Press-fit Connector and Temperature Rise Curve	20 21
Ordering Information	21
C B C S E R I E S	
CBC Series Introduction	22
Technical Characteristics	23
Contact Variants	24
Standard Shell Assembly	25
Ordering Information	26
CBDD/ CBHD SERIES	
CBDD/CBHD Series Introduction and Technical Characteristics	27-28
Contact Variants	28
Standard Shell Assembly	29
Code 21 Solder Cup Connector and	
Code 3, 35, 36 and 37 Straight Printed Board Mount Connector	30
Code 4, 45 and 47 Right Angle (90°) Printed Board Mount Connector	31-33
Code 65 Straight Printed Board Mount Connector with FDS4201D or MDS4201D Shielded Contacts and	0.4
Code 84 Right Angle (90°) Printed Board Mount Connector with FRT4201D or MRT4201D Shielded Contacts	34
Code 93 Compliant Press-Fit Connector	35
Printed Board Mount Contact Hole Pattern	36
Ordering Information	37-38

TABLE OF CONTENTS



C B C D S E R I E S	
CBCD Series Introduction	39 39-40 40 41 42
CBDPB/CBDPC SERIES	
Combo-Dual Port Series Introduction Technical Characteristics Contact Variants Right Angle (90°) Printed Board Mount Connector Right Angle (90°) Printed Board Mount Contact Hole Pattern Ordering Information	43 43-44 44 45 46-47 48
CONNECTOR SAVERS	
ACBDP/ACBMP Series Introduction Technical Characteristics ACBDP/ACBMP Series Size 20 and Size 8 Contact Variants Male to Female Connector Saver and Jackscrew Systems Ordering Information	57 58 58 59 60
UNIQUE FEATURES	
Unique Features Introduction and Sequential Mating Contacts Size 8 Contact Stabilization Feature Combo-D Connectors with 100 AMP High Current Removable Crimp Power Contacts Technical Characteristics	61 62
and 100 AMP High Current Removable Crimp Power Contacts (for use with 8 AWG wire)	63
High Current Removable Crimp Power Contacts and Temperature Rise Curve	64 65
Size 8 Right Angle (90°) Printed Board Mount High Voltage Contact	65
Size 8 Bus Bar Power Contacts	66 66
Customer Specified Contact Termination Length	67

continued on next page . . .


TABLE OF CONTENTS



REMOVABLE CONTACTS	
Removable Contact Technical Characteristics What makes PosiBand® contact interface significant Size 22 Crimp and Removable Signal Crimp Contacts Size 22 Removable Thermocouple Signal Crimp Contact Size 20 Crimp and Removable Crimp Signal Contact Size 20 Removable Thermocouple Crimp Signal Contact Size 16 Removable Crimp Power Contacts Size 8 Removable Crimp Power Contacts Size 8 Removable Solder Cup Power Contacts Size 8 Removable High Voltage Power Contacts Size 8 Straight Printed Board Mount Power Contact Size 8 Removable Shielded Contact Size 8 Removable Shielded Contact Size 8 Removable Shielded Contact Size 8 Right Angle (90°) Printed Board Mount Shielded Contact Size 8 Right Angle (90°) Printed Board Shielded Contact	68-69 69 70-71 71 72-73 74 74 75 75 76 76 77 78 79
SPECIAL OPTIONS	
Modification (MOS) Suffixes	81
APPLICATION TOOLS	
Introduction Contact Reels for Automatic Pneumatic Crimp Tools Contact Application Tools Cross Reverence List Suggested Printed Board Hole Sizes For Compliant Press-Fit Connectors Compliant Press-Fit Connector Installation Tools	82 82 83-84 85 86
Q P L L I S T I N G	
Positronic offers a wide variety of QPL connector products	87

TEMPERATURE RISE CURVES FOR SIZE 8, 10 AND 12 AWG WIRE





Test conducted in accordance with UL1977. All power contacts under load.

MC4008D: Curve developed using a mated CBD7W2F57 8 AWG and CBC7W2M loaded with MC4008D contacts

terminated to 8 AWG wire.

MC4010D: Curve developed using a mated CBD7W2F36 and CBC7W2M loaded with MC4010D contacts 10 AWG

terminated to 10 AWG wire.

MC4012D: Curve developed using a mated CBD7W2F55 12 AWG and CBC7W2M loaded with MC4012D contacts

terminated to 12 AWG wire.


Test conducted in accordance with UL1977. All power contacts under load.

MC4008D: Curve developed using a mated CBD21WA4F57 and CBC21WA4M loaded with MC4008D contacts 8 AWG terminated to 8 AWG wire

Curve developed using a mated CBD21WA4F36 MC4010D: 10 AWG and CBC21WA4M loaded with MC4010D contacts terminated to 10 AWG wire.


Curve developed using a mated CBD21WA4F55 MC4012D: and CBC21WA4M loaded with MC4012D contacts terminated to 12 AWG wire.

21WA4



TEMPERATURE RISE (°C)

8W8



Test conducted in accordance with UL1977. All power contacts under load.

MC4008D: Curve developed using a mated CBD8W8F57 and CBC8W8M loaded with MC4008D contacts 8 AWG terminated to 8 AWG wire.

Curve developed using a mated CBD8W8F36 MC4010D: 10 AWG and CBC8W8M loaded with MC4010D contacts terminated to 10 AWG wire.

MC4012D: Curve developed using a mated CBD8W8F55 and CBC8W8M loaded with MC4012D contacts 12 AWG

terminated to 12 AWG wire.


TEMPERATURE RISE (°C)

GENERAL INFORMATION



TEMPERATURE RISE CURVE FOR STANDARD AND HIGH CONDUCTIVITY CONTACT MATERIAL





Test conducted in accordance with UL1977. All power contacts under load.

Standard Material: Curve developed using a mated CBD3W3F

loaded with FC4008D contacts and CBD3W3M loaded with MC4008D contacts

terminated to 8 AWG wire.

High Conductivity:

Curve developed using a mated CBD3W3F loaded with FC4008DS contacts and CBD3W3M loaded with MC4008DS con-

tacts terminated to 8 AWG wire.

Test conducted in accordance with UL1977. All power contacts under load.

Curve developed using a mated CBD8W8F Standard Material:


loaded with FC4008D contacts and CBD8W8M loaded with MC4008D contacts

terminated to 8 AWG wire.

High Conductivity:


Curve developed using a mated CBD8W8F loaded with FC4008DS contacts and CBD8W8M loaded with MC4008DS contacts terminated to

8 AWG wire.



TEMPERATURE RISE (°C)

HIGH DENSITY 8W2



Test conducted in accordance with UL1977. All power contacts under load.

Standard Material: Curve developed using a mated

CBCD8W2M loaded with

MC112N/AA-133.0 contacts and CBCD8W2S loaded with FC112N4/AA con-

tacts terminated to 12 AWG wire.

Curve developed using a mated **High Conductivity:**

CBCD8W2M loaded with

MC112NS-133 0 contacts and CBCD8W2S loaded with FC112N4S/AA contacts termi-

nated to 12 AWG wire.

^{*} indicates contact gender

^{*} indicates contact gender

Positronic connectpositronic.com

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO STANDARD DENSITY PCB MOUNT

Combo-D D-Sub

Size 20 Fixed Signal and Thermocouple Contacts

Size 8 Removable Power, Shielded, Air and High Voltage Contacts

UL Recognized CSA Recognized File #E49351 File #LR54219 DSCC 85039

Telecommunication UL File #E140980

Combo-D series connectors permit mixed contact combinations of power, shielded, air, high voltage and signal contacts within the same connector body. Twenty-two connector variants are offered in six standard shell sizes.

Three performance levels of Combo-D series connectors are offered: professional, industrial and military. CBD series connectors are quality connectors recommended for use in sheltered, non-corrosive indoor and outdoor environments having normal ventilation, but without temperature or humidity controls. Signal contacts are offered with open entry professional level or PosiBand closed entry industrial level signal contacts. CBD series connectors meet performance requirements of IEC 60807-2, Performance Level One or Two. CBM series connectors are military quality connectors recommended for use in sheltered, mildly corrosive environments having a wide range of temperature, pressure and humidity changes. CBM series connectors will meet the applicable performance requirements of DSCC 85039.

Combo-D series connectors utilize precision machined signal contacts. Connector variants are available with contact terminations for solder and straight and right angle (90°) printed board mount terminations featuring a choice



of inch or metric printed board footprints.

Power, shielded and high voltage contacts are removable, having solder and straight and right angle (90°) printed board mount terminations. Power and shielded contacts are available with crimp terminations. Air contact options are also available, see page 80 for details.

For low level shielding requirements, ferrite inductors may be attached to both signal and power contacts of connectors having contact terminations which are straight or right angle (90°) for printed board mounting applications. For additional information contact Technical Sales.

The female power contacts feature the Large Surface Area (L.S.A.) closed entry contact design which provides maximum mating surfaces between male and female contacts and reduced contact resistance during operation.

A wide assortment of printed board mounting hardware, cable support hoods, and locking systems is available from stock.

A blind mating system is available for applications requiring connector coupling in recessed areas or mobile power coupling systems.

Straight and right angle (90°) PCB mount thermocouple contacts are available, please contact Technical Sales for details.

Combo-D D-Sub

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO STANDARD DENSITY PCB MOUNT



TECHNICAL CHARACTERISTICS

MATERIALS AND FINISHES:

Insulator: Glass filled polyester per ASTM D 5927

UL 94V-0, blue color, and composite.

Contacts: Precision machined copper alloy.

Contact Plating:

SIGNAL: Gold flash over nickel plate and gold 0.000050

[1.27µ] over nickel plate. Other finishes available upon request, see page 81.

POWER: Gold flash over nickel. Other finishes available

upon request, see page 81.

SHIELDED: For contact platings, see page 68. **HIGH VOLTAGE:** For contact platings, see page 68.

Steel with tin plate; zinc plate; stainless Shells: steel passivated. Other materials and finishes

available upon request.

Mounting Spacers Nylon; polyester; copper alloy or steel with zinc and Brackets: plate or tin plate; phosphor bronze with tin

plate; stainless steel, passivated.

Push-On Fasteners: Phosphor bronze and beryllium copper with

tin plate.

Jackscrew Systems: Brass or steel with zinc plate or clear zinc

plate or tin plate; stainless steel, passivated.

Hoods: Composite and plastic, UL 94V-0; brass or

steel with zinc plate. Aluminum; aluminum with electroless nickel plate. For aluminum hoods, zinc content is 1% maximum. Die cast

zinc.

Non-magnetic versions are available, contact Technical Sales.

MECHANICAL CHARACTERISTICS:

Signal Contacts,

Fixed:

Size 20 contacts, male - 0.040 inch [1.02mm] diameter. CBD series has open entry female contacts. PosiBand closed entry female options are also available. CBM series has PosiBand closed entry female contacts,

see page 68 for details.

Contact Retention Signal: 9 lbs. [40N]. Power, shielded in Insulator: and high voltage: 22 lbs [98N]. Resistance to 500°F [260°C] for 10 seconds duration

Solder Iron Heat: per IEC 60512-6.

Signal Contact Solder contacts - 0.042 inch [1.06mm] minimum hole diameter for 20 AWG [0.5 mm²] Terminations:

wire maximum.

Straight Printed Board Mount - 0.028 inch

[0.71mm] termination diameter.

Right Angle (90°) Printed Board Mount -0.028 inch [0.71 mm] termination diameter.

Power Contacts, Removable, Crimp or Solder Termination: Size 8 contact, male – 0.142 inch [3.61mm] mating diameter. Terminations for 6, 8, 10, 12, and 16 AWG. Female contact features

Large Surface Area (L.S.A.) closed entry contact design utilizing BeCu mechanical retention member. Closed crimp barrel.

Power Contacts, **Printed Board Mount:**

Size 8 contact, male - 0.142 inch [3.61mm] mating diameter. Printed board terminations with 0.078 inch [1.98mm], 0.094

inch [2.39mm] and 0.125 inch [3.18mm]

termination diameters.

Shielded Contacts, Removable:

See table of cable sizes for contact termination dimensions, page 78.

High Voltage Contacts:

Straight and right angle (90°) terminations -0.041 inch [1.04mm] minimum hole diameter.

Shells:

Male shells may be dimpled for EMI/ESD

ground paths.

Polarization: Trapezoidally shaped shells and polarized jackscrews.

Mounting to Jackscrews and riveted fasteners with Angle Brackets: 0.120 inch [3.05mm] diameter hole, and

threaded riveted fasteners with 4-40 threads

and nvlon inserts.

Mounting to Rapid installation push-on fasteners and

Printed Board: threaded posts.

Locking Systems: Jackscrews and vibration locking systems. Mechanical Operations: CBD series, open entry contacts, 500

operations. CBD series, PosiBand closed entry and CBM series, 1,000 operations. Per

IEC 60512-5.

ELECTRICAL CHARACTERISTICS:

SIZE 20 CONTACTS

Contact Current Rating: 7.5 amperes nominal. Initial Contact Resistance: 0.008 ohms maximum.

Proof Voltage: 1000 V r.m.s.

SIZE 8 CONTACTS

POWER CONTACTS

Contact Current Rating - Tested per UL 1977:

Standard Contact Material:

0.078 inches diameter / 12 AWG terminations: 39 amperes. 0.094 inches diameter / 10 AWG terminations: 50 amperes. 0.125 inches diameter / 8 AWG terminations: 70 amperes.

See Temperature Rise Curves on page 1 for details.

High Conductivity Contact Material:

8 AWG terminations: 80 amperes.

See Temperature Rise Curves on page 2 for details.

Initial Contact Resistance:

Standard Contact Material: 0.0005 ohms max. per IEC 60512-2,

Test 2b.

5 G ohms.

High Conductivity 0.00035 ohms max. per IEC 60512-2,

Contact Material: Test 2b. Proof Voltage: 1000 V r.m.s.

SHIELDED CONTACTS

For electrical characteristics, see page 69.

HIGH VOLTAGE CONTACTS

For electrical characteristics, see page 69.

CONNECTOR

Insulation Resistance:

Clearance and

Creepage Distance: 0.039 [1.0mm] minimum.

Working Voltage: 300 V r.m.s.

CLIMATIC CHARACTERISTICS:

-55°C to +125°C. Temperature Range:

Damp Heat, Steady State: 10 days.

THERMOCOUPLE CONTACTS:

Straight and right angle PCB mount contacts are available, please contact Technical Sales for details.

Size 20 crimp contacts are available in CBC series, see page 74 for details.

Combo-D D-Sub

CONTACT VARIANTS

FACE VIEW OF MALE OR REAR VIEW OF FEMALE

Note: Connectors can be kitted with all applicable removable contacts, SHELL SIZE 1 contact Technical Sales for connector part number. SHELL SIZE 2 -3W3 *2 3WK3 **7W2** SHELL SIZE 3 -00000000 00000000 000000 00000 21W1 5W5 9W4 13W3 17W2 SHELL SIZE 4 -0000 8W8 13W6 17W5 21WA4 25W3 27W2 **SHELL SIZE 5** 24W7 36W4 43W2 47W1 SHELL SIZE 6 -


Notes:

*12WK2 connectors have 1 male and 1 female contacts. Female connector should be loaded with female contact in A2 position.


46W4


*23WK3 male variant contains 2 male contacts and 1 female contact. Female variant contains 2 female contacts and 1 male contact













OPTIONAL SHELL ASSEMBLY (0, 02) Ø0.120±0.005 [Ø3.05±0.13] Mounting hole, two places for stainless steel shell (0 option) Ø0.154 [3.91] Mounting hole, two places (02 option)




SHELL SIZES	A <u>±0.015</u> [0.38]	B <u>±0.005</u> [0.13]	B1 <u>±0.005</u> [0.13]	C ±0.005 [0.13]	D <u>±0.005</u> [0.13]	D1 <u>±0.005</u> [0.13]	E <u>±0.015</u> [0.38]	G <u>±0.010</u> [0.25]	H <u>±0.010</u> [0.25]	K ±0.005 [0.13]	M <u>±0.010</u> [0.25]
SHELL SIZE 1 MALE	<u>1.213</u> [30.81]		<u>0.666</u> [16.92]	<u>0.984</u> [24.99]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
SHELL SIZE 1 FEMALE	<u>1.213</u> [30.81]	<u>0.643</u> [16.33]		<u>0.984</u> [24.99]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 2 MALE	1.541 [39.14]		<u>0.994</u> [25.25]	1.312 [33.32]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	1.083 [27.51]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
SHELL SIZE 2 FEMALE	<u>1.541</u> [39.14]	<u>0.971</u> [24.66]		<u>1.312</u> [33.32]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>1.083</u> [27.51]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 3 MALE	<u>2.088</u> [53.04]		1.534 [38.96]	1.852 [47.04]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	<u>1.625</u> [41.28]	<u>0.422</u> [10.72]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 3 FEMALE	2.088 [53.04]	<u>1.511</u> [38.38]		<u>1.852</u> [47.04]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>1.625</u> [41.28]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 4 MALE	2.729 [69.32]		2.182 [55.42]	2.500 [63.50]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	<u>2.272</u> [57.71]	<u>0.422</u> [10.72]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 4 FEMALE	<u>2.729</u> [69.32]	<u>2.159</u> [54.84]		2.500 [63.50]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>2.272</u> [57.71]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 5 MALE	2.635 [66.93]		2.079 [52.81]	<u>2.406</u> [61.11]		<u>0.441</u> [11.20]	<u>0.605</u> [15.37]	2.178 [55.32]	<u>0.534</u> [13.56]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 5 FEMALE	2.635 [66.93]	2.064 [52.43]		<u>2.406</u> [61.11]	<u>0.423</u> [10.74]		<u>0.605</u> [15.37]	2.178 [55.32]	<u>0.534</u> [13.56]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 6 MALE	2.729 [69.32]		2.212 [56.18]	2.500 [63.50]		<u>0.503</u> [12.78]	<u>0.668</u> [16.97]	2.302 [58.47]	<u>0.596</u> [15.14]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 6 FEMALE	<u>2.729</u> [69.32]	2.189 [55.60]		2.500 [63.50]	<u>0.485</u> [12.32]		<u>0.668</u> [16.97]	2.302 [58.47]	<u>0.596</u> [15.14]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]


Combo-D D-Sub

SOLDER CUP CONNECTOR CODE 2





For solder cup contacts, specify codae 2 in step 4 of ordering information.



Typical part number: CBD7W2M200T0



CBD17W2F200E0 with FS4008D contacts.

CBD17W2M55B30T20


STRAIGHT PRINTED BOARD MOUNT CONNECTOR

CODE 3, 35, 36 AND 37

For Code 93 Press-Fit Board Mount Connectors, see page 20.

CONTACT CODE	DØ
3	
35	<u>0.078</u> [1.98]
36	<u>0.094</u> [2.39]
37	<u>0.125</u> [3.18]

For straight printed board mount contacts, specify code no. in step 4 of ordering information.



Typical part number: CBD17W2F35S60T2X

Combo-D D-Sub

Fixed female jackscrews

Specify code 5

or 55 in step 4 of

ordering information.

Typical part number:

CBD17W2M55R7NT20

0.220 [5.59] Max.

0.220 [5.59] Max

±0.008

0.112

[2.84]


Тур.

0.339 [8.61]

D


PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO STANDARD DENSITY PCB MOUNT






See temperature rise curves on pages 1 and 2

CBD***R7*** 0.283 [7.19] CONTACT EXTENSION										
SHELL SIZE	A	В	С	D						
SHELL SIZE 1	<u>1.204</u>	<u>0.984</u>	<u>0.339</u>	<u>0.283</u>						
	[30.58]	[24.99]	[8.61]	[7.19]						
SHELL SIZE 2	<u>1.532</u>	<u>1.312</u>	<u>0.339</u>	<u>0.283</u>						
	[38.91]	[33.32]	[8.61]	[7.19]						
SHELL SIZE 3	<u>2.072</u>	<u>1.852</u>	<u>0.339</u>	<u>0.283</u>						
	[52.63]	[47.04]	[8.61]	[7.19]						
SHELL SIZE 4	<u>2.720</u>	<u>2.500</u>	<u>0.339</u>	<u>0.283</u>						
	[69.09]	[63.50]	[8.61]	[7.19]						
SHELL SIZE 5	<u>2.626</u>	<u>2.406</u>	<u>0.395</u>	<u>0.283</u>						
	[66.70]	[61.11]	[10.03]	[7.19]						





CBD36W4F55R7NT2X

RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR WITH 0.125 [3.18] Ø POWER CONTACTS

ODE 5 AND 57, 0.283 [7,19] CONTACT EXTENSION

		T '	See to	-		on rages 1 a		JON
			CBD***R7*	** 0.283 [7.	.19] CONT	ACT EXTEN	SION	
			SHELL SIZE	Α	В	С	D	
Fixed female		A	SHELL SIZE 1	<u>1.204</u> [30.58]	<u>0.984</u> [24.99]	<u>0.339</u> [8.61]	<u>0.283</u> [7.19]	
jackscrews		0.008 B	SHELL SIZE 2	<u>1.532</u> [38.91]	<u>1.312</u> [33.32]	<u>0.339</u> [8.61]	<u>0.283</u> [7.19]	
			SHELL SIZE 3	<u>2.072</u> [52.63]	<u>1.852</u> [47.04]	<u>0.339</u> [8.61]	<u>0.283</u> [7.19]	
			SHELL SIZE 4	<u>2.720</u> [69.09]	<u>2.500</u> [63.50]	<u>0.339</u> [8.61]	<u>0.283</u> [7.19]	
Ħ		<u> </u>	SHELL SIZE 5	<u>2.626</u> [66.70]	<u>2.406</u> [61.11]	<u>0.395</u> [10.03]	<u>0.283</u> [7.19]	0.810 20.57
Specify code 5 or 57 in step 4 of pordering information.	0.810 - [20.57] -	1	Push-on faste		of female.	7 0.125 (3.18) 6	0.112 [2.84] Typ. 0.112 [2.84] Typ.	
	W2M57R7NT20	0.170 [4 Nominal	.32] beryllium copp	oer.	_		тур	ical part number: D36W4F57R7NT2X




Combo-D D-Sub

SHELL SIZE 6

RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR WITH 0.078 [1.98] Ø POWER CONTACTS

CODE 5 AND 55, 0.283 [7.19] CONTACT EXTENSION

CONNECTOR VARIANT 46W4




SHELL SIZE 6

RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR WITH 0.125 [3.18] Ø POWER CONTACTS

CODE 5 OR 57, 0.283 [7.19] CONTACT EXTENSION


CONNECTOR VARIANT 46W4




Combo-D D-Sub

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO STANDARD DENSITY PCB MOUNT








Combo-D D-Sub

RIGHT ANGLE (90°) PRINTED BOARD CONTACT HOLE PATTERN WITH 0.078 [1.98] Ø POWER CONTACTS AND STRAIGHT PRINTED BOARD CONTACT HOLE PATTERN WITH 0.078 [1.98] Ø, 0.094 [2.39] Ø AND 0.125 [3.18] Ø POWER CONTACTS

HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR; USE MIRROR IMAGE FOR FEMALE CONNECTOR.

MOUNT CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROWS.



NOTE: For suggested printed board recommended drill hole sizes, plating and finished hole sizes for compliant contact termination positions, see page 85.

For press-fit connector installation tools, see page 86.


Suggest 0.045 [1.14] Ø hole for signal contact termination positions.


Suggest 0.045 [1.14] Ø hole for signal contact termination positions. Suggest 0.098 [2.49] Ø hole for 0.078 [1.98] Ø power contact termination positions. Suggest 0.114 [2.90] Ø hole for 0.094 [2.39] Ø power contact termination positions. Suggest 0.145 [3.68] Ø hole for 0.125 [3.18] Ø power contact termination positions. Suggest 0.123 ±0.003 [3.12] Ø hole for mounting connector with push-on fasteners.





RIGHT ANGLE (90°) PRINTED BOARD CONTACT HOLE PATTERN WITH 0.078 [1.98] Ø POWER CONTACTS AND STRAIGHT PRINTED BOARD CONTACT HOLE PATTERN WITH 0.078 [1.98] Ø, 0.094 [2.39] Ø AND 0.125 [3.18] Ø POWER CONTACTS


HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR; USE MIRROR IMAGE FOR FEMALE CONNECTOR. MOUNT CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROWS.


















47W1



CODE NO.	x	Y	A	В		
3						
35	<u>0.112</u>	0.056	<u>0.050</u>	<u>0.100</u>		
36	[2.84]	[1.42]	[1.27]	[2.54]		
37						
5	<u>0.112</u>	0.056	<u>0.056</u>	<u>0.112</u>		
55	[2.84]	[1.42]	[1.42]	[2.84]		
7	0.100	0.050	0.050	0.100		
75	[2.54]	[1.27]	[1.27]	[2.54]		

SUGGESTED PRINTED BOARD HOLE SIZES:

Suggest 0.045 [1.14] Ø hole for signal contact termination positions. Suggest 0.098 [2.49] Ø hole for 0.078 [1.98] Ø power contact termination positions. Suggest 0.114 [2.90] Ø hole for 0.094 [2.39] Ø power contact termination positions. Suggest 0.145 [3.68] Ø hole for 0.125 [3.18] Ø power contact termination positions. Suggest 0.123 ±0.003 [3.12] Ø hole for mounting connector with push-on fasteners.


NOTE: For suggested printed board recommended drill hole sizes, plating and finished hole sizes for compliant contact termination positions, see page 85.

For press-fit connector installation tools, see page 86.



Combo-D D-Sub


RIGHT ANGLE (90°) PRINTED BOARD CONTACT HOLE PATTERN WITH 0.125 [3.18] Ø POWER CONTACTS








RIGHT ANGLE (90°) PRINTED BOARD CONTACT HOLE PATTERN WITH 0.125 [3.18] Ø POWER CONTACTS


HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR; USE MIRROR IMAGE FOR FEMALE CONNECTOR. MOUNT CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROWS.















47W1







CODE NO.	5 & 57	7 & 77
A	<u>0.471</u> [11.96]	<u>0.390</u> [9.91]
В	<u>0.415</u> [10.54]	0.340 [8.64]
С	<u>0.359</u> [9.12]	0.290 [7.37]
x	<u>0.112</u> [2.84]	<u>0.100</u> [2.54]
Y	<u>0.056</u> [1.42]	<u>0.050</u> [1.27]

Combo-D D-Sub

STRAIGHT PRINTED BOARD MOUNT CONNECTOR WITH FDS4201D OR MDS4201D SHIELDED CONTACTS CODE 65




RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR WITH FRT4201D OR MRT4201D SHIELDED CONTACTS CODE 85



CBD**85**** 0.283 [7.19] CONTACT EXTENSION										
SHELL SIZE	A	В	С	D						
SHELL SIZE 1	<u>1.204</u>	<u>0.984</u>	<u>0.339</u>	<u>0.283</u>						
	[30.58]	[24.99]	[8.61]	[7.19]						
SHELL SIZE 2	<u>1.532</u>	<u>1.312</u>	<u>0.339</u>	<u>0.283</u>						
	[38.91]	[33.32]	[8.61]	[7.19]						
SHELL SIZE 3	<u>2.072</u>	<u>1.852</u>	<u>0.339</u>	<u>0.283</u>						
	[52.63]	[47.04]	[8.61]	[7.19]						
SHELL SIZE 4	<u>2.720</u>	<u>2.500</u>	<u>0.339</u>	<u>0.283</u>						
	[69.09]	[63.50]	[8.61]	[7.19]						
*1SHELL SIZE 5	<u>2.626</u>	<u>2.406</u>	<u>0.395</u>	<u>0.545</u>						
	[66.70]	[61.11]	[10.03]	[13.84]						

*1NOTE:


Shell size 5 connectors are supplied inverted when ordered with right angle (90°) printed board mount shielded contacts.





STRAIGHT PRINTED BOARD MOUNT CONTACT HOLE PATTERN WITH FDS4201D AND MDS4201D SHIELDED CONTACTS


HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR: USE MIRROR IMAGE FOR FEMALE CONNECTOR.





Combo-D
D-Sub


STRAIGHT PRINTED BOARD MOUNT CONTACT HOLE PATTERN WITH FDS4201D AND MDS4201D SHIELDED CONTACTS


HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR; USE MIRROR IMAGE FOR FEMALE CONNECTOR.


















RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONTACT HOLE PATTERN WITH FRT4201D AND MRT4201D SHIELDED CONTACTS


HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR; USE MIRROR IMAGE FOR FEMALE CONNECTOR. MOUNT CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROWS.





Combo-D D-Sub

RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONTACT HOLE PATTERN WITH FRT4201D AND MRT4201D SHIELDED CONTACTS

HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR; USE MIRROR IMAGE FOR FEMALE CONNECTOR. MOUNT CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROWS.







*1 <u>NOTE</u>:


Shell size 5 connectors are supplied inverted when ordered with right angle (90°) printed board mount shielded contacts.

*1 47W1



COMPLIANT PRESS-FIT CONNECTOR **CODE 93**

Positronic recommends the practice of using mounting hardware to secure connector to printed circuit board.



SUGGESTED PRINTED BOARD HOLE SIZES:


Suggest 0.123 [3.12] Ø hole for connector mounting holes.

NOTE: For suggested printed board recommended drill hole sizes, plating and finished hole sizes for compliant contact termination positions, see page 85.

For press-fit connector installation tools, see page 86.

FOR STRAIGHT PRINTED BOARD CONTACT HOLE PATTERNS, SEE PAGES 11 AND 12.

TEMPERATURE RISE CURVE



Test conducted in accordance with UL1977. All power contacts under load.

Curve developed using CBD8W8M00000 and CBD8W8F93S000 connectors with MC4008D contacts terminated to 8 AWG wire.



Combo-D D-Sub

ORDERING INFORMATION - CODE NUMBERING SYSTEM

Specify Complete Connector By Selecting An Option From Step 1 Through 8

	Opecity	Complet	e Com	ector by	OGIGCIII	ig Air (Splion	110111	жер і	mougi	10
STEP	1	2	3	4	5	6	7	8	9		10
EXAMPLE	CBD	17W2	F	55	R7	N	T2	Х	/AA	_	-14
STEP 1 - BASIC SERIES										*2 STEI	P 10 - SPECIAL OPTIONS
CBD – Professional/Industrial C see Step 3.										FOR SF	ECIAL OPTIONS, SEE L OPTIONS APPENDIX
CBM - Military conformance w "closed entry" female si tacts plated 0.000050 [gold over nickel plate. 0 "S" or "M" in Step 3.	gnal con- 1.27µ]									FOR OF THE FO Other Sp	CT TECHNICAL SALES RDERING DETAILS OF LLOWING: Decial Requirements.
STEP 2 - CONNECTOR \	/ARIANT	S									/ Right Angle Thermocouple ount contacts.
Shell Size 1 - 2WK2, 5W1										PCBII	iourit contacts.
Shell Size 2 - 3W3, 3WK3, 7W	2, 11W1										
Shell Size 3 - 5W5, 9W4, 13W3											/IRONMENTAL
Shell Size 4 - 8W8, 13W6, 17V	V5, 21WA4,	,									ICE OPTIONS
25W3, 27W2	14/0 47/4/4								/AA	- RoHS C	ompliant
Shell Size 5 - 24W7, 36W4, 43 Shell Size 6 - 46W4	VV2, 47 VV I								legisla	tion is not	ance to environmental required, this step will not be CBD17W2F55R7NT2X
STEP 3 - CONNECTOR (GENDER										
F - Female - Professional Lev								_		IELL OP	TIONS
Open Entry Sigr M - Male	nal Contacts	3							 Zinc P 		a a a in vata d
S - Female - Industrial / Milita	rv Level -								– Stairii – Tin Pla		passivated.
PosiBand Close		nal Contact	s								impled (male connectors only).
STEP 4 - CONTACT TERM	IINIATION	I TVDE					*2 STE	ЕР 7 - I	OCKI	NG AND	POLARIZING SYSTEMS
0 - Connector ordered without	size 8 powe	er, shielded,		h voltage			0 -	None.			panel mounted.
removable contacts. See pa numbers. Available on 2WK							V5 -	Lock T	ab, conn ab, conn	ector rear	panel mounted.
2 – Fixed Solder Cup, Signal Co			na ovvo.				VL -	Lock L	ever, use	ed with Hoo	ods only.
3 - Solder, Straight Printed Boa	rd Mount w	ith Signal C	Contacts,	0.170			T2 -	Fixed F	emale Ja emale Ja	ackscrews. ackscrews.	
[4.32] Tail Length. 35 – Solder, Straight Printed Boa	rd Mount w	ith Sianal a	nd 0 078	[1 08] (7							larized Jackscrews.
Power Contacts, 0.170 [4.3]	2] Tail Leng	th.								ackscrews	
36 – Solder, Straight Printed Boa	rd Mount w	ith Signal a	nd 0.094	[2.39] Ø			E2 -	Rotatin	g Male S a Male w	crew Lock	s. I Hex for 3/32 Hex Drives
Power Contacts, 0.170 [4.3] 37 – Solder, Straight Printed Boa			nd 0 125	[3 18] Ø							Polarized Jackscrews.
Power Contacts, 0.170 [4.3]	21 Tail Leng	th.				*2 CTE		IOODS	AND	DITEL O	N FASTENERS
5 – Solder, Right Angle (90°) Pri	nted Board	Mount with	n Signal C	ontacts		1		10003	AND	-USH-U	N FASTENERS
only, 0.283 [7.19] Signal Co 55 – Solder, Right Angle (90°) Prir			Signal and	1 0 078			NoneLightwe	eiaht Δlur	minum H	ood, nicke	l finish
[1.98] Ø Power Contacts, 0.2	283 [7.19] S	Signal Conta	ıct Extensi	on.		AC	 Lightwe 	eight Alur	minum H	ood, no fir	ish.
57 - Solder, Right Angle (90°) Prir						Z					t extended height, plastic and
[3.18] Ø Power Contacts, 0.2 65 – Solder, Straight Printed Board						Ι н					crews, shell sizes 1 through 5 zes 2 through 5
MDS/FDS 4201D footprint, 0.	170 [4.32] 5	Signal Conta	ct Tail Len	ath.		*3 G	- Hood, I	EMI/RĖI,	Die Cast	Zinc, shel	l sizes 1 through 6
7 – Solder, Metric System Right	Angle (90°)) Printed Bo	oard Mour	nt		N ·	Push-o	n Fasten	er, for Ri	ght Angle	(90°) Mounting Brackets
with Signal Contacts only, 0 75 - Solder, Metric System Right Ar	ngle (90°) Pri	nted Board N	Mount with	Signal and	*2STE	P 5 - N	/OUNT	ING ST	YLE		
0.078 [1.98] Ø Power Contacts 77 – Solder, Metric System Right	s, 0.370 [9.4 Anglo (00°)	0] Signal Co	ntact Exter	nsion.			ng Hole, 0				
with Signal and 0.125 [3.18]					02 -	 Mountir 	ng Hole, 0	.154 [3.9	1] Ø	°) Metal wit	n Cross Bar

- **B3 Bracket, Mounting, Right Angle (90°) Metal with Cross Bar **5B8 Bracket, Mounting, Right Angle (90°) Plastic with Cross Bar
- - Float Mounts, Universal
 - Threaded Post, Brass, 0.250 [6.35] Length
 Threaded Post, Nylon, 0.250 [6.35] Length
- P2
- *5 R2 - Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Thread Fixed Female Jackscrews with Cross Bar
- *5 R6 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 0.120 [3.05] Ø Mounting Hole with Cross Bar
- *5 R7 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Threads with Cross Bar
- *5 R8 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Locknut with Cross Bar
 - Swaged Spacer, 4-40 Threads, 0.250 [6.35] Length, Spacer length changes to 0.265 [6.73] when used in conjunction with Code 93 contacts
- Swaged Spacer, 4-40 Threads, 0.125 [3.18] Length
- Swaged Locknut, 4-40 Threads S5
- Swaged Spacer with Push-on Fastener, 4-40 Threads, 0.250 [6.35] Length

NOTES

*1 Not available on shell size 6, CBD 46W4.

termination length 0.225 [5.72].

Contact Extension.

Contact Extension.

- *2 For additional information on accessories listed in steps 5, 6, 7 and 10, see Accessory Catalog.
- *3 When using G hood with CBD variants, use the extended height hood. See Accessories Catalog for extended G hood options.

Solder, Right Angle (90°) Printed Board Mount with Signal and

93 - Size 20 Omega type compliant and Size 8 Bi-Spring type compliant,

Shielded Contacts MRT/FRT 4201D footprint, 0.283 [7.19] Signal

- *4 For stainless steel dimpled male versions, contact Technical Sales.
- *5 Not available when using 2WK2, 3W3, 3WK3, 5W5, 8W8, instead use B, R, R3, R4, or R5.
 - **DIMENSIONS ARE IN INCHES [MILLIMETERS].** ALL DIMENSIONS ARE SUBJECT TO CHANGE.

Size 8 Removable Power, Shielded, Air and High Voltage Contacts

DSCC 85039 IEC 60807-3 **UL Recognized CSA Recognized** File #E49351 File #LR54219 Telecommunication UL File #E140980



CBC series connectors offer professional, industrial and military performance levels. Connectors are designed for use in sheltered, mildly corrosive environments having a wide range of temperature, pressure and humidity changes. CBC series connectors offer mixed crimp-removable contact combinations of power, shielded, air, high voltage, signal, and thermocouple contacts within the same connector body. Refer to size 8 removable contacts power, shielded, air and high voltage section, pages 68-80 for technical characteristics. Sixteen connector variants are offered in six standard shell sizes.

A wide assortment of cable support hoods and locking systems is available from stock.

CBC series connectors also offer a Blind Mating connector system for applications requiring connector couplings in recessed areas or for mobile power coupling systems.

CBC series connectors utilize precision machined contacts and they meet the applicable performance and dimensional requirements of IEC 60807-3, Performance Levels One and Two, DSCC 85039 and MIL-DTL-24308.

Connectors Designed To Customer Specifications

Positronic Combo-D connectors can be modified to customers specifications.

Examples: select loading of contacts for cost savings or to gain creepage and clearance distances; longer PCB terminations; customer specified hardware; sealing for water resistance.

Contact Technical Sales with your particular requirements.

Positronic connectoositronic connectoositronic

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO STANDARD DENSITY CRIMP REMOVABLE CONTACTS

Combo-D D-Sub

TECHNICAL CHARACTERISTICS

MATERIALS AND FINISHES:

Insulator: Glass filled polyester per ASTM D 5927, UL

94V-0, blue color.

Contacts: Precision machined copper alloy.

SIGNAL: Gold flash over nickel plate and gold 0.000050 [1.27µ] over nickel plate.

Other finishes available upon request,

see page 81.

POWER: Gold flash over nickel. Other finishes

available upon request, see page 81.

SHIELDED: For contact platings, see page 68.

HIGH VOLTAGE: For contact platings, see page 68.

Shells: Steel with tin plate; zinc plate; stainless steel passivated. Other materials and

finishes available upon request.

Mounting Spacers: Nylon; copper alloy or steel with zinc plate or tin plate; phosphor bronze with tin plate;

stainless steel, passivated.

Jackscrew Systems: Brass or steel with zinc plate or clear

zinc plate or tin plate; stainless steel,

passivated.

Hoods: Composite and plastic UL94V-0; brass or

steel with zinc plate. Aluminum; aluminum with electroless nickel plate. For aluminum hoods, zinc content is 1% maximum. Die

cast zinc.

Non-magnetic versions are available, contact Technical Sales.

MECHANICAL CHARACTERISTICS:

Signal Contacts,

Crimp Removable: Size 20 contacts, male – 0.040 inch

[1.02mm] mating diameter; Female rugged open entry or PosiBand closed entry contact design, see page 69 for details.

Contact Retention

In Insulator: Signal: 9 lbs. [40N]. Power, shielded and

high voltage: 22 lbs. [98N]

Crimp Contact

Terminations: Closed barrel crimp, wire sizes 18 AWG

[1.0mm²] through 30 AWG [0.05 mm²]

Power Contacts, Removable, Crimp

or Solder Termination: Size 8 contacts, male – 0.142 inch [3.61 mm]

mating diameter. Terminations for 6, 8, 10, 12, and 16 AWG. Female contact features Large Surface Area (L.S.A.) closed entry contact design utilizing BeCu mechanical retention member. Closed crimp barrel.

Shielded Contacts,

Removable: See table of cable sizes for contact

termination dimensions, page 78.

High Voltage Contacts: Straight and right angle (90°) terminations –

0.041 inch [1.04mm] min. hole diameter.

Shells: Male shells may be dimpled for EMI/ESD

ground paths.

Polarization: Trapezoidally shaped shells and polarized

jackscrews.

Locking Systems: Jackscrews and vibration locking systems.

Mechanical Operations: 500 operations for open entry contact,

1000 operations for PosiBand closed entry contact with 0.000050 [1.27 μ] gold plating.

Per IEC 60512-5.

ELECTRICAL CHARACTERISTICS:

SIZE 20 CONTACTS

Contact Current Rating: 7.5 amperes nominal. Initial Contact Resistance: 0.008 ohms maximum.

1000 V r.m.s.

Proof Voltage: SIZE 8 CONTACTS

POWER CONTACTS

For electrical characteristics, see page 4.

SHIELDED CONTACTS

For electrical characteristics, see page 69.

HIGH VOLTAGE CONTACTS

For electrical characteristics, see page 69.

CONNECTOR

Insulation Resistance: 5 G ohms.

Clearance and

Creepage Distance: 0.039 [1.0mm] minimum.

Working Voltage: 300 V r.m.s.


CLIMATIC CHARACTERISTICS:

Temperature Range: -55°C to +125°C. **Damp Heat. Steady State:** 10 days.

THERMOCOUPLE CONTACTS:

Size 20 crimp contacts are available. See page 74 for details.

PCB mount contacts are available in CBD/CBM series, see page 4 for details.



CBC11W1M10Z00 WITH MS4012D CONTACT

CBC11W1S100T20 WITH FC4008D CONTACT

*1 CONTACT VARIANTS

FACE VIEW OF MALE OR REAR VIEW OF FEMALE

NOTES:


- *1 Additional contact variants may be tooled at customer request.
- *2 13W6 and 27W2 variant currently available in female only. Contact Technical Sales for availability of male connector.





SHELL SIZE 2

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.















Combo-D D-Sub


STANDARD SHELL ASSEMBLY














SHELL SIZES	A ±0.015 [0.38]	B <u>±0.005</u> [0.13]	B1 <u>±0.005</u> [0.13]	C <u>±0.005</u> [0.13]	D <u>±0.005</u> [0.13]	D1 <u>±0.005</u> [0.13]	E <u>±0.015</u> [0.38]	G <u>±0.010</u> [0.25]	H <u>±0.010</u> [0.25]	K <u>±0.005</u> [0.13]	M ±0.010 [0.25]
SHELL SIZE 1 MALE	1.213 [30.81]		<u>0.666</u> [16.92]	<u>0.984</u> [24.99]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
SHELL SIZE 1 FEMALE	1.213 [30.81]	<u>0.643</u> [16.33]		<u>0.984</u> [24.99]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 2 MALE	<u>1.541</u> [39.14]		<u>0.994</u> [25.25]	<u>1.312</u> [33.32]		0.329 [8.36]	<u>0.494</u> [12.55]	1.083 [27.51]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
SHELL SIZE 2 FEMALE	1.541 [39.14]	<u>0.971</u> [24.66]		<u>1.312</u> [33.32]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	1.083 [27.51]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 3 MALE	2.088 [53.04]		1.534 [38.96]	<u>1.852</u> [47.04]		0.329 [8.36]	<u>0.494</u> [12.55]	1.625 [41.28]	<u>0.422</u> [10.72]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 3 FEMALE	2.088 [53.04]	1.511 [38.38]		<u>1.852</u> [47.04]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	1.625 [41.28]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 4 MALE	2.729 [69.32]		<u>2.182</u> [55.42]	2.500 [63.50]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	<u>2.272</u> [57.71]	<u>0.422</u> [10.72]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 4 FEMALE	2.729 [69.32]	<u>2.159</u> [54.84]		2.500 [63.50]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>2.272</u> [57.71]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 5 MALE	<u>2.635</u> [66.93]		<u>2.079</u> [52.81]	<u>2.406</u> [61.11]		<u>0.441</u> [11.20]	<u>0.605</u> [15.37]	<u>2.178</u> [55.32]	<u>0.534</u> [13.56]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 5 FEMALE	<u>2.635</u> [66.93]	<u>2.064</u> [52.43]		<u>2.406</u> [61.11]	<u>0.423</u> [10.74]		<u>0.605</u> [15.37]	<u>2.178</u> [55.32]	<u>0.534</u> [13.56]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
SHELL SIZE 6 MALE	<u>2.729</u> [69.32]		<u>2.212</u> [56.18]	<u>2.500</u> [63.50]		<u>0.503</u> [12.78]	<u>0.668</u> [16.97]	<u>2.302</u> [58.47]	<u>0.596</u> [15.14]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]
SHELL SIZE 6 FEMALE	<u>2.729</u> [69.32]	<u>2.189</u> [55.60]		<u>2.500</u> [63.50]	<u>0.485</u> [12.32]		<u>0.668</u> [16.97]	<u>2.302</u> [58.47]	<u>0.596</u> [15.14]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]

Combo-D D-Sub

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO STANDARD DENSITY CRIMP REMOVABLE CONTACTS



ORDERING INFORMATION - CODE NUMBERING SYSTEM

Specify Complete Connector By Selecting An Option From Step 1 Through 8

STEP	1	2	3	4	5	6	7	8	9		10		
EXAMPLE	СВС	7W2	M	1	0	Z	0	0	/AA	_	-14		
TEP 1 - BASIC S	ERIES											PECIAL OPTIO	
TEP 2 - CONNEC hell Size 1 W1 hell Size 2	TOR VA	RIANTS								SPECI		PPTIONS, SEE INS APPENDIX	
W2, 11W1 Shell Size 3 W4, 13W3, 17W2, 21W1 Shell Size 4 113W6, 21WA4, 25W3, *127W2 Shell Size 5 24W7, 36W4, 43W2, 47W1									/AA NOTE	TEP 9 - ENVIRONMENTAL COMPLIANCE OPTIONS 'AA - RoHS Compliant OTE: If compliance to environmental gislation is not required, this step will not be used. Example: OBC7W2M10Z00			
hell Size 6 6W4 TEP 3 - CONNECTOR GENDER 1- Male - Female - Industrial or Military Level								0 - *4 S - X -	Zinc PlatStainlesTin Plate	B - SHELL OPTIONS Zinc Plated. Stainless Steel, passivated. Tin Plated. Tin Plated and Dimpled (male connectors only)			
PosiBand ofessional Level female ailable and can be orde	Closed Ent open entry or red separate	, 0					*2 STI					NG SYSTEMS	
STEP 4 - CONTACT TERMINATION TYPE 0 - Connector ordered without contacts. Order signal, power, shielded, high voltage, air and thermocouple contacts separately. See pages 68-80 for contact part numbers. 1 - Signal contacts, 20 AWG-24 AWG [0.5mm²-0.25mm²]. 11 - Signal contacts, 20 AWG-24 AWG [0.5mm²-0.25mm²] with MC/FC 4012D Power Contact. 12 - Signal contacts, 20 AWG-24 AWG [0.5mm²-0.25mm²].						V3 - V5 - VL - T - T2 - T6 - E - E2 - E3 -	 None. Lock Tab, connector front panel mounted. Lock Tab, connector rear panel mounted. Lock Lever, used with Hoods only. Fixed Female Jackscrews. Fixed Female Jackscrews. Fixed Male and Female Polarized Jackscrews. Rotating Male Jackscrews. Rotating Male Screw Locks. Rotating Male with Internal Hex for 3/32 Hex Drives Rotating Male and Female Polarized Jackscrews. 						
0.25mm ²] with	MC/FC 4	016D pow	er contact			_	EP 6 - H 0 - None	OODS					

*2 STEP 5 - MOUNTING STYLE

- 0 Mounting Hole, 0.120 [3.05] Ø
- 02 Mounting Hole, 0.154 [3.91] Ø
- F Float Mounts, Universal
- S2 Swaged Spacer, 4-40 Threads, 0.125 [3.18] Length

0.25mm²] with MCC/FCC 4101D shielded contacts.

14 - Signal contacts, 20 AWG-24 AWG [0.5mm²-0.25mm²]

with MCC/FCC 4102D shielded contacts.

S5 - Swaged Locknut, 4-40 Threads

NOTES

- *1 Connector variant 13W6 and 27W2 are currently available in female only, contact Technical Sales for availability of male connector.
- *2 For additional information on accessories listed in steps 5, 6, 7 and 10, see Accessory Catalog.
- *3 When using G hood with CBC variants, use the extended height hood. See Accessories Catalog for extended G hood options.
- *4 For stainless steel dimpled male versions, contact Technical Sales.

For crimping information and crimp tools, see Application Tools section, page 82.

- Hood, Top Opening, Metal, shell sizes 2 through 5
- AN Lightweight Aluminum Hood, nickel finish.
- AC Lightweight Aluminum Hood, no finish.
- Hood, EMI/RFI, Die Cast Zinc, shell sizes 1 through 6
 Hood, Top or Side Opening, robust extended height, plastic and composite, with rotating jackscrews, shell sizes 1 through 5



Combo-D D-Sub

Size 22 Fixed Signal and Thermocouple Contacts

Size 16 Fixed Power Contacts

Size 8 Removable Power, Shielded, Air and High Voltage Contacts

UL and CSA Recognition, for status contact Technical Sales

Positronic's Combo-D connectors are a popular choice for a wide variety of applications. Many options make the Combo-D a versatile connector choice.

CBDD high density series connectors are quality connectors recommended for use in sheltered, non-corrosive indoor and outdoor environments having normal ventilation, but without temperature or humidity controls.

CBDD series connectors offer mixed contact combinations of power, signal, and thermocouple contacts within the same connector body.

CBDD series connectors utilize precision machined contacts offering high reliability. Connector variants are available with straight and right angle (90°) printed board mount terminations, including compliant press-fit. For cable connectors see CBCD section, page 39.

Female power contacts feature the Large Surface Area (L.S.A.)



closed entry contact design, which provides maximum mating surfaces between male and female contacts and reduced contact resistance during operation.

Fixed signal contacts are available with open entry female contacts, professional level or PosiBand closed entry female contacts, industrial level. Military contact plating is optional.

A wide assortment of printed board mounting hardware, cable support hoods, and locking systems is available from stock.

A blind mating system is available for applications requiring connector coupling in recessed areas or mobile power coupling systems.

Straight and right angle PCB mount thermocouple contacts are available, please contact Technical Sales for details.

CBDD series connectors utilize precision machined contacts and meet applicable performance and dimensional requirements of IEC 60807-7, MIL-DTL-24308 and AS39029.

TECHNICAL CHARACTERISTICS

MATERIALS AND FINISHES:

Insulator: Glass filled polyester per ASTM D 5927

UL 94V-0, blue color.

Contacts: Precision machined copper alloy.

Contact Plating:

SIGNAL: Gold flash over nickel plate. Other finishes available upon request, see page 81.

POWER: Gold flash over nickel. Other finishes available

upon request, see page 81.

SHIELDED: For contact platings, see page 68.

HIGH VOLTAGE: For contact platings, see page 68.

Shells: Steel with tin plate; zinc plate; stainless steel

passivated. Other materials and finishes

available upon request.

Mounting Spacers
And Brackets:

Nylon; polyester; copper alloy or steel with zinc plate or tin plate; phosphor bronze with tin plate;

stainless steel, passivated.

Push-On Fasteners: Phosphor bronze and beryllium copper with tin

plate.

Jackscrew Systems: Brass or steel with zinc plate or clear zinc plate

or tin plate; stainless steel, passivated. Composite and plastic, UL 94V-0; brass or

Hoods: Composite and plastic, UL 94V-0; brass or steel with zinc plate. Aluminum; aluminum with electroless nickel plate. For aluminum hoods,

zinc content is 1% maximum. Die cast zinc.

Non-magnetic versions are available, contact Technical Sales.

MECHANICAL CHARACTERISTICS:

Signal Contacts,

Fixed: Size 22 contacts, male – 0.030 inch

[0.76mm] mating diameter. Female – open entry or PosiBand closed entry design, see

page 69 for details.

Power Contacts,

Fixed: Size 16 contacts, male – 0.0625 inch

[1.588mm] mating diameter. Female contacts

- closed entry design.

Size 8 contacts, male - 0.142 inch [3.61mm] mating diameter. Female contact features Large Surface Area (L.S.A.) closed entry contact design utilizing BeCu mechanical retention member. Closed crimp barrel.

Contact Retention in Insulator:

SIGNAL SIZE 22 5 lbs. [21N] minimum POWER SIZE 16 6 lbs [26N] minimum

SIZE 8 22 lbs [98N] for power, shielded and high

oltage.

Resistance to 500°F [260°C] for 10 seconds duration per **Solder Iron Heat:** IEC 60512-6.

Signal Contact Solder contacts - 0.035 inch [0.89mm]
Terminations: minimum hole diameter for 22 AWG

[0.3 mm²] wire maximum.

Straight Printed Board Mount - 0.020 inch

[0.51mm] diameter.

Combo-D D-Sub

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO HIGH DENSITY PCB MOUNT



TECHNICAL CHARACTERISTICS, continued

continued from previous page. . . .

Right Angle (90°) Printed Board Mount -

0.030 inch [0.76 mm] diameter.

Power Contacts,

Size 16 contacts- printed board terminations Terminations: with 0.063 inch [1.60mm] diameters.

Size 8 contacts - printed board terminations with 0.078 inch [1.98mm], 0.094 inch [2.39mm] and 0.125 inch [3.18mm]

termination diameters.

Shielded Contacts,

Removable: See table of cable sizes for contact

termination dimensions, page 78.

High Voltage Contacts: Straight and right angle (90°) terminations -0.041 inch [1.04mm] minimum hole diameter.

Shells: Male shells may be dimpled for EMI/ESD

ground paths.

Trapezoidally shaped shells and polarized Polarization:

jackscrews.

Mounting to

Angle Brackets: Jackscrews and riveted fasteners with 0.120

inch [3.05mm] diameter hole, and threaded riveted fasteners with 4-40 threads and nylon

Mounting to

Printed Board: Rapid installation push-on fasteners and

threaded posts.

Locking Systems: Jackscrews and vibration locking systems.

Open entry, 500 operations. PosiBand closed Mechanical Operations:

entry, 1000 operations minimum. Per IEC

ELECTRICAL CHARACTERISTICS:

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

SHELL SIZE 3 —

*2 15W4

Eleven Size 22 Signal Contacts

and Four Size 8 Power Contacts

SIZE 22 CONTACT

Contact Current Rating: 5 amperes nominal.

Initial Contact Resistance: 0.010 ohms maximum for open entry 0.005 ohms maximum for closed entry

Proof Voltage: 1000 V r.m.s.

SIZE 16 CONTACTS

POWER CONTACTS

Contact Current Rating - Tested per UL 1977:

Standard Contact Material: 28 amperes. **High Conductivity Contact Material:** 40 amperes.

See Temperature Rise Curves on page 2 for details.

Initial Contact Resistance:

Standard Contact Material: 0.0016 ohms max. Per IEC

60512-2. Test 2b.

High Conductivity

Contact Material: 0.001 ohms max. Per IEC

60512-2, Test 2b. 1000 V r.m.s.

SIZE 8 CONTACTS

Proof Voltage:

POWER CONTACTS

For electrical characteristics, see page 4.

SHIELDED CONTACTS

For electrical characteristics, see page 69.

HIGH VOLTAGE CONTACTS

For electrical characteristics, see page 69.

CONNECTOR

Insulation Resistance: 5 G ohms.

Clearance and

Creepage Distance: 0.042 inch [1.06mm] minimum.

Working Voltage: 300 V r.m.s.

CLIMATIC CHARACTERISTICS:

-55°C to +125°C. Temperature Range:

Damp Heat, Steady State: 10 days.

THERMOCOUPLE CONTACTS:

Straight and right angle PCB mount contacts are available, please contact

Technical Sales for details.

Size 22 crimp contacts are available in CBCD series, see page 71 for

*1 CONTACT VARIANT

FACE VIEW OF MALE OR REAR VIEW OF FEMALE

- SHELL SIZE 1 -



8W2

Six Size 22 Signal Contacts and Two Size 16 Power Contacts

SHELL SIZE 4 —



*345W2

Forty-three Size 22 Signal Contacts and Two Size 8 Power Contacts






Eighteen Size 22 Signal Contacts and One Size 8 Power Contact

NOTES:


- *1 Additional contact variants may be tooled at customer request.
- *2 For technical, dimensional and PCB layout information on 15W4 variants, contact Technical Sales.
- *3 45W2 variant currently available in male only. Contact Technical Sales for availability of female connector.






Combo-D D-Sub


STANDARD SHELL ASSEMBLY







CBDD8W2M3S000

CBDD45W2M30000









SHELL SIZES	VARIANT	A <u>±0.015</u> [0.38]	B <u>±0.005</u> [0.13]	B1 ±0.005 [0.13]	C <u>±0.005</u> [0.13]	D <u>±0.005</u> [0.13]	D1 <u>±0.005</u> [0.13]	E <u>±0.015</u> [0.38]	G <u>±0.010</u> [0.25]	H <u>±0.010</u> [0.25]	K <u>±0.005</u> [0.13]	M ±0.010 [0.25]
	8W2M	<u>1.213</u> [30.81]		<u>0.666</u> [16.92]	<u>0.984</u> [24.99]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
1	8W2F 8W2S	1.213 [30.81]	<u>0.643</u> [16.33]		<u>0.984</u> [24.99]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
2	19W1M	1.541 [39.14]		<u>0.994</u> [25.25]	1.312 [33.32]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	1.083 [27.51]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
	19W1F 19W1S	1.541 [39.14]	0.971 [24.66]		1.312 [33.32]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	1.083 [27.51]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
4	45W2M	<u>2.729</u> [69.32]		2.182 [55.42]	2.500 [63.50]		0.329 [8.36]	<u>0.494</u> [12.55]	<u>2.272</u> [57.71]	<u>0.422</u> [10.72]	<u>0.230</u> [5.84]	<u>0.426</u> [10.82]

SOLDER CUP CONNECTOR CODE 21





Typical part number: CBDD19W1M2100T0

STRAIGHT PRINTED BOARD MOUNT CONNECTOR


CODE 3, 35, 36, AND 37

CONTACT CODE	DØ
3	


For straight printed board mount contacts, specify code 3 in step 4 of ordering information.

CONTACT CODE	DØ
3	
35	<u>0.078</u> [1.98]
36	<u>0.094</u> [2.39]
37	<u>0.125</u> [3.18]

For straight printed board mount contacts, specify code no. in step 4 of ordering information.



Typical part number: CBDD8W2F3S60T2X




Typical part number: CBDD19W1F35S60T2X



PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO HIGH DENSITY PCB MOUNT


RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR SIZE 16 POWER CONTACTS WITH 0.063 [1.60] Ø TERMINATIONS CODE 4, 0.314 [7.98] CONTACT EXTENSION

See temperature rise curves on pages 1 and 2




RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR SIZE 8 POWER CONTACTS WITH 0.078 [1.98] Ø TERMINATIONS CODE 4 AND 45, 0.314 [7.98] CONTACT EXTENSION

See temperature rise curves on pages 1 and 2




RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR SIZE 8 POWER CONTACTS WITH 0.078 [1.98] Ø TERMINATIONS **CODE 4 AND 45, 0.314 [7.98] CONTACT EXTENSION**


See temperature rise curves on pages 1 and 2



RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR SIZE 8 POWER CONTACTS WITH 0.125 [3.18] Ø TERMINATIONS **CODE 4 AND 47, 0.314 [7.98] CONTACT EXTENSION**

See temperature rise curves on pages 1 and 2






Typical part number: CBDD19W1M47R70T20



PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO HIGH DENSITY PCB MOUNT

RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR SIZE 8 POWER CONTACTS WITH 0.125 [3.18] Ø TERMINATIONS CODE 4 AND 47, 0.314 [7.98] CONTACT EXTENSION

See temperature rise curves on pages 1 and 2




Connectors Designed To Customer Specifications

Positronic Combo-D connectors can be modified to customers specifications.


Examples: select loading of contacts for cost savings or to gain creepage and clearance distances; longer PCB terminations; customer specified hardware; sealing for water resistance.

Contact Technical Sales with your particular requirements.

STRAIGHT PRINTED BOARD MOUNT CONNECTOR WITH FDS4201D OR MDS4201D SHIELDED CONTACTS **CODE 65**




RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR WITH FRT4201D OR MRT4201D SHIELDED CONTACTS **CODE 84**





PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO HIGH DENSITY PCB MOUNT


RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR WITH FRT4201D OR MRT4201D SHIELDED CONTACTS **CODE 84**




CBDD45W2M84R70T20

COMPLIANT PRESS-FIT CONNECTOR **CODE 93**

Positronic recommends the practice of using mounting hardware to secure connector to printed circuit board.




TYPICAL PART NUMBER: CBDD8W2M93S0T20



TYPICAL PART NUMBER: CBDD19W1M93S0T20

PRINTED BOARD MOUNT CONTACT HOLE PATTERN

HOLE IDENTIFICATION SHOWN FOR MALE CONNECTOR; USE MIRROR IMAGE FOR FEMALE CONNECTOR. MOUNT RIGHT ANGLE (90°) CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROWS.



CBDD/CBHD SERIES



PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO HIGH DENSITY PCB MOUNT

Combo-D D-Sub

ECIAL OPTIONS PTIONS, SEE

ICAL SALES ETAILS OF rements. ngle Thermocouple

ORDERING INFORMATION - CODE NUMBERING SYSTEM

Specify Complete Connector By Selecting An Option From Step 1 Through 8

FOR CONNECTORS NOT INCLUDING SIZE 8 CONTACTS

STEP	1	2	3	4	5	6	7	8	9		10
EXAMPLE	CBDD	8W2	M	93	S	0	0	0	/AA		-14
										*2 STE	EP 10 - SPECIAL OPTIO
STEP 1 - BASIC SEI CBDD Series - CBHD Series - High Cone									FOR SPECIAL OPTIONS, SE SPECIAL OPTIONS APPEND ON PAGE 81.		
Power Co	ntacts	ANITE								FOR C	ACT TECHNICAL SALES ORDERING DETAILS OF OLLOWING:
STEP 2 - CONNECTOR VARIANTS Shell Size 1 - 8W2										Straigh	Special Requirements. It and Right Angle Thermocoupl
See next page for order		ation								PC	B mount contacts
for other shell size opti	ons.								STE	P 9 - FN	IVIRONMENTAL
STEP 3 - CONNECT	OR GENI	DER	J								NCE OPTIONS
*1 F - Female - Profession									/AA	- RoHS	Compliant
Open Enti M - Male	ry Signal Co	ntacts									liance to environmental
*1S - Female - Industrial PosiBand	/ Military Lev Closed Entr		ontacts						legisla used.	etion is no Example:	t required, this step will not be CBDD8W2M93S000
STEP 4 - CONTACT	TERMIN	ATION T	YPE	-				STE	P 8 - SH	HELL OF	PTIONS
*521 – Fixed Solder Cup, *53 – Solder, Straight Pri length. *54 – Solder, Right Angle [7.98] Signal Conta	inted Board e (90°) Printe	Mount, 0.4 ed Board N	170 [4.32]	Tail				*4 S X	- Tin Pla	ess Steel, ated.	passivated. Dimpled (male connectors only)
93 – Signal Omega type compliant, termina *2 STEP 5 - MOUNT	e compliant a tion length 0	and Power 0.225 [5.72		type			0 - V3 -	NoneLock	Tab, con	nector fro	POLARIZING SYSTEMS Int panel mounted. It panel mounted.

STEP 5 - MOUNTING STYLE

- Mounting Hole, 0.120 [3.05] Ø

- Mounting Floie, 0.126 [0.05] 5
 Mounting Hole, 0.126 [3.91] 5
 Bracket, Mounting, Right Angle (90°) Metal with Cross Bar
 Bracket, Mounting, Right Angle (90°) Plastic with Cross Bar
- Float Mounts, Universal

- Hoat Mourits, Oniversal
 Threaded Post, Brass, 0.250 [6.35] Length
 Threaded Post, Nylon, 0.250 [6.35] Length
 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Thread Fixed Female Jackscrews with Cross Bar
- Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 0.120 [3.05] Ø Mounting Hole with Cross Bar
- Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Threads with Cross Bar
- Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector
- with 4-40 Locknut with Cross Bar

 Swaged Spacer, 4-40 Threads, 0.250 [6.35] Length, Spacer length changes to 0.265 [6.73] when used in conjunction with Code 93 contacts
- Swaged Spacer, 4-40 Threads, 0.125 [3.18] Length
- Swaged Locknut, 4-40 Threads
- Swaged Spacer with Push-on Fastener, 4-40 Threads, 0.250 [6.35] Length

connectors only).

- nted.
- VĹ Lock Lever, used with Hoods only.
- Fixed Female Jackscrews.
- T2 Fixed Female Jackscrews.
- Fixed Male and Female Polarized Jackscrews. T6
- Rotating Male Jackscrews.
- Rotating Male Screw Locks.
 Rotating Male with Internal Hex for 3/32 Hex Drives
- Rotating Male and Female Polarized Jackscrews.

*2 STEP 6 - HOODS AND PUSH-ON FASTENERS

- 0 None
- AN Lightweight Aluminum Hood, nickel finish
- AC Lightweight Aluminum Hood, no finish
- H Hood, Top Opening, Metal
- *3G Hood, EMI/RFI, Die Cast Zinc
- N Push-on Fastener, for Right Angle (90°) Mounting Brackets
- Hood, Top or Side Opening, robust extended height, plastic and composite, with rotating male jackscrews

NOTES

- *1 Power contacts are always supplied with "Closed Entry" female contacts.
- *2 For additional information on accessories listed in steps 5, 6, 7 and 10, see Accessory Catalog.
- *3 When using G hood with CBDD variants, use the extended height hood. See Accessories Catalog for extended G hood options.
- *4 For stainless steel dimpled male versions, contact Technical Sales
- *5 Size 16 power contact are included.

Combo-D D-Sub

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO HIGH DENSITY PCB MOUNT



ORDERING INFORMATION - CODE NUMBERING SYSTEM

Specify Complete Connector By Selecting An Option From Step 1 Through 8

FOR CONNECTORS INCLUDING SIZE 8 CONTACTS

EXAMPLE CBDD STEP 1 - BASIC SERIES CBDD Series - CBHD Series - High Conductivity Power Contacts STEP 2 - CONNECTOR VARIA Shell Size 2 - 19W1 *6 Shell Size 3 - 15W4 *1 Shell Size 4 - 45W2 STEP 3 - CONNECTOR GENI *2 F - Female - Professional Level - Open Entry Signal Co M - Male *2 S - Female - Industrial / Military Level - PosiBand Closed Entre	DER	3 M	93	5 S	0	7 0	0	9 /AA	**3 STEP 10 - SPECIAL OPTIONS FOR SPECIAL OPTIONS, SEE SPECIAL OPTIONS APPENDIX ON PAGE 81. CONTACT TECHNICAL SALES FOR ORDERING DETAILS OF THE FOLLOWING: Other Special Requirements. Straight and Right Angle Thermocouple PCB mount contacts
CBDD Series - CBHD Series - High Conductivity Power Contacts STEP 2 - CONNECTOR VARIA Shell Size 2 - 19W1 ** Shell Size 3 - 15W4 ** Shell Size 4 - 45W2 STEP 3 - CONNECTOR GENI ** F - Female - Professional Level - Open Entry Signal Co M - Male ** S - Female - Industrial / Military Lev	DER								FOR SPECIAL OPTIONS, SEE SPECIAL OPTIONS APPENDIX ON PAGE 81. CONTACT TECHNICAL SALES FOR ORDERING DETAILS OF THE FOLLOWING: Other Special Requirements. Straight and Right Angle Thermocouple
CBHD Series - High Conductivity Power Contacts STEP 2 - CONNECTOR VARIA Shell Size 2 - 19W1 *6 Shell Size 3 - 15W4 *1 Shell Size 4 - 45W2 STEP 3 - CONNECTOR GENI *2 F - Female - Professional Level - Open Entry Signal Co M - Male *2 S - Female - Industrial / Military Level	DER								SPECIAL OPTIONS APPÉNDIX ON PAGE 81. CONTACT TECHNICAL SALES FOR ORDERING DETAILS OF THE FOLLOWING: Other Special Requirements. Straight and Right Angle Thermocouple
Shell Size 2 - 19W1 *6 Shell Size 3 - 15W4 *1 Shell Size 4 - 45W2 STEP 3 - CONNECTOR GENI *2 F - Female - Professional Level - Open Entry Signal Co M - Male *2 S - Female - Industrial / Military Lev	DER								FOR ORDERING DETAILS OF THE FOLLOWING: Other Special Requirements. Straight and Right Angle Thermocouple
								CC	P 9 - ENVIRONMENTAL DMPLIANCE OPTIONS - RoHS Compliant
STEP 4 - CONTACT TERMIN. 21 - Fixed Solder Cup, 22 AWG-30 3 - Solder, Straight Printed Board	y Signal Co ATION T AWG [0.3r	/PE nm²-0.05n					STEE	legisla used.	E: If compliance to environmental tion is not required, this step will not be Example: CBDD8W2M93S000
 0.170 [4.32] Tail Length. 35 - Solder, Straight Printed Board [1.98] Ø Power Contacts, 0.17 36 - Solder, Straight Printed Board [2.39] Ø Power Contacts, 0.17 37 - Solder, Straight Printed Board 	Mount with 0 [4.32] Tai Mount with 0 [4.32] Tai	Signal an I Length. Signal an I Length.	d 0.078 d 0.094				*5 S	Zinc PStainleTin Pla	lated. ss Steel, passivated.
 [3.18] Ø Power Contacts, 0.17 4 – Solder, Right Angle (90°) Printe Contacts, 0.314 [7.98] Signal (45 – Solder, Right Angle (90°) Printe and 0.078 [1.98] Ø Power Cor Contact Extension. 47 – Solder, Right Angle (90°) Printe and 0.125 [3.18] Ø Power Cor Signal Contact Extension. 65 – Solder, Straight Printed Board Shielded Contacts MDS/FDS Signal Contact Tail Length. 84 – Solder, Right Angle (90°) Printe and Shielded Contacts MRT/F [7.98] Signal Contact Extension 93 – Signal Omega type compliant a compliant, termination length 0 	0 [4.32] Tai de Board M. Contact Ext de Board M. tacts, 0.31. de Board M. tacts, 0.31. Mount with 201D footp de Board M. RT 4201D fo.	I Length. ount with a ension. ount with a 4 [7.98] Si ount with a 4 [7.98] Signal an orint, 0.170 ount with a footprint, 0	Signal Signal Ignal Signal d 0 [4.32] Signal 0.314			0 V3 V5 VL T T2 T6 E E2 E3 E6 STEP 6 0 - Nor N - Ligh	- None Lock - Lock - Lock - Fixed - Fixed - Rotati - R	Tab, conicate the control of the con	nector front panel mounted. nector rear panel mounted. nector rear panel mounted. ned with Hoods only. ackscrews. ackscrews. I Female Polarized Jackscrews. Jackscrews. Screw Locks. with Internal Hex for 3/32 Hex Drives and Female Polarized Jackscrews. D PUSH-ON FASTENERS In Hood, nickel finish In Hood, no finish

- 0 Mounting Hole, 0.120 [3.05] Ø 02 Mounting Hole, 0.154 [3.91] Ø B3 Bracket, Mounting, Right Angle (90°) Metal with Cross Bar B8 Bracket, Mounting, Right Angle (90°) Plastic with Cross Bar

- Bracket, Mounting, night Angle (80) induction.
 Float Mounts, Universal
 Threaded Post, Brass, 0.250 [6.35] Length
 Threaded Post, Nylon, 0.250 [6.35] Length
 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Thread Fixed Female Jackscrews with Cross Bar
- Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 0.120 [3.05] Ø Mounting Hole with Cross Bar
 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector R6
- with 4-40 Threads with Cross Bar
- Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector R8 with 4-40 Locknut with Cross Bar
- Swaged Spacer, 4-40 Threads, 0.250 [6.35] Length, Spacer length changes to 0.265 [6.73] when used in conjunction with Code 93 contacts
- Swaged Spacer, 4-40 Threads, 0.125 [3.18] Length
- Swaged Locknut, 4-40 Threads
- Swaged Spacer with Push-on Fastener, 4-40 Threads, 0.250 [6.35]

- *4 G Hood, EMI/RFI, Die Cast Zinc
- N Push-on Fastener, for Right Angle (90°) Mounting Brackets
- Z Hood, Top or Side Opening, robust extended height, plastic and composite, with rotating male jackscrews

NOTES

- *1 45W2 variant currently available in male only.
- *2 Power contacts are always supplied with "Closed Entry" female contacts.
- *3 For additional information on accessories listed in steps 5, 6, 7 and 10, see Accessory Catalog.
- *4 When using G hood with CBDD variants, use the extended height hood. See Accessories Catalog for extended G hood options.
- *5 For stainless steel dimpled male versions, contact Technical Sales.
- *6 For technical, dimensional and PCB layout information on 15W4 variants, con-




Combo-D D-Sub

Size 22 Removable Signal and Thermocouple Crimp Contacts

Size 16 Removable Power Contacts

Size 8 Removable Power, Shielded, Air and High Voltage Contacts

UL and CSA Recognition, for status contact Technical Sales



CBCD high density series connectors are quality connectors designed for use in sheltered, mildly corrosive environments having a wide range of temperature, pressure and humidity changes. CBCD series connectors offer mixed crimp-removable contact combinations of power, signal, and thermocouple contacts within the same connector body.

A wide assortment of cable support hoods and locking systems is available from stock.

CBCD series connectors also offer a blind mating connector system for applications requiring connector couplings in recessed areas or for mobile power coupling systems.

CBCD series connectors utilize precision machined contacts and meet applicable performance and dimensional requirements of IEC 60807-7, MIL-DTL-24308 and AS39029.

TECHNICAL CHARACTERISTICS

MATERIALS AND FINISHES:

Insulator: Glass filled polyester per ASTM D 5927

UL 94V-0, blue color.

Contacts: Precision machined copper alloy.

Contact Plating:

SIGNAL: Gold flash over nickel plate and gold 0.000050

[1.27µ] over nickel plate. Other finishes available

upon request, see page 81.

POWER: Gold flash over nickel. Other finishes available

upon request, see page 81.

SHIELDED: For contact platings, see page 68. For contact platings, see page 68.

Shells: Steel with tin plate; zinc plate; stainless steel

passivated. Other materials and finishes

available upon request.

Mounting Spacers: Copper alloy or steel with zinc plate or tin

plate; stainless steel, passivated.

Jackscrew Systems: Brass or steel with zinc plate or clear zinc plate or tin plate; stainless steel, passivated.

Composite and plastic, UL 94V-0; brass or

steel with zinc plate. Aluminum; aluminum with electroless nickel plate. For aluminum hoods, zinc content is 1% maximum. Die cast

zinc.

Non-magnetic versions are available, contact Technical Sales.

MECHANICAL CHARACTERISTICS:

Signal Contacts,

Crimp Removable: Size 22 contacts, male – 0.030 inch

[0.76mm] mating diameter. Terminations for 20, 22, 24, 26, 28 and 30 AWG. Female PosiBand closed entry design, see page 69 for details. Closed crimp

barrel.

Power Contacts,

Crimp Removable: Size 16 contacts, male – 0.0625 inch

[1.588mm] mating diameter. Terminations for 12, 14, 16, 18, 20, 22, and 24 AWG. Female closed entry design. Closed

crimp barrel.

Size 8 contacts, male – 0.142 inch [3.61mm] mating diameter. Terminations for 6, 8, 10, 12, and 16 AWG. Female contact features Large Surface Area (L.S.A.) closed entry contact design utilizing BeCu mechanical retention member. Closed crimp barrel.

Contact Retention In Insulator:

SIGNAL SIZE 22 9 lbs. [40N]. **POWER SIZE 16** 15 lbs. [67N]

POWER SIZE 8 22 lbs. [98N] - power, shielded and

high voltage.

Hoods:



TECHNICAL CHARACTERISTICS, continued

continued from previous page. . . .

MECHANICAL CHARACTERISTICS, continued:

Shells: Male shells may be dimpled for EMI/ESD

ground paths.

Polarization: Trapezoidally shaped shells and polarized

iackscrews.

Locking Systems: Jackscrews and vibration locking systems.

Mechanical Operations: 1000 operations minimum per IEC 60512-5.

ELECTRICAL CHARACTERISTICS:

SIZE 22 CONTACTS

Contact Current Rating: 5 amperes nominal. Initial Contact Resistance: 0.005 ohms maximum. 1000 V r.m.s. Proof Voltage:

SIZE 16 CONTACTS

POWER CONTACTS

Contact Current Rating - Tested per UL 1977:

Standard Contact Material: 28 amperes. **High Conductivity Contact Material:** 40 amperes. See Temperature Rise Curves on page 2 for details.

Initial Contact Resistance:

Standard Contact Material: 0.0016 ohms max. Per IEC 60512-

2, Test 2b.

High Conductivity

Contact Material: 0.001 ohms max. Per IEC 60512-2,

Test 2b.

Proof Voltage: 1000 V r.m.s.

SIZE 8 CONTACTS

POWER CONTACTS

For electrical characteristics, see page 4.

SHIELDED CONTACTS

For electrical characteristics, see page 69.

HIGH VOLTAGE CONTACTS

For electrical characteristics, see page 69.

CONNECTOR

Insulation Resistance: 5 G ohms

Clearance and

Creepage Distance: 0.042 inch [1.06mm] minimum.

Working Voltage: 300 V r.m.s.

CLIMATIC CHARACTERISTICS:

Temperature Range: -55°C to +125°C.

Damp Heat, Steady State: 10 days.

THERMOCOUPLE CONTACTS:

Size 22 crimp contacts are available. See page 71 for details.

PCB mount contacts are available in CBDD series, see page 27 for

*1 CONTACT VARIANT


FACE VIEW OF MALE OR REAR VIEW OF FEMALE

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

- SHELL SIZE 1 -


SHELL SIZE 2 -

SHELL SIZE 4 -




8W2

Six Size 22 Signal Contacts and Two Size 16 Power Contacts



Eighteen Size 22 Signal Contacts and One Size 8 Power Contact



Forty-three Size 22 Signal Contacts and Two Size 8 Power Contacts


NOTES:

- *1 Additional contact variants may be tooled at customer request.
- *245W2 variant currently available in female only. Contact Technical Sales for availability of male connector.




Combo-D **D-Sub**


STANDARD SHELL ASSEMBLY









TYPICAL CONNECTOR TOP VIEW







SHELL SIZES	VARIANT	A <u>±0.015</u> [0.38]	B <u>±0.005</u> [0.13]	B1 <u>±0.005</u> [0.13]	C ±0.005 [0.13]	D <u>±0.005</u> [0.13]	D1 <u>±0.005</u> [0.13]	E <u>±0.015</u> [0.38]	G <u>±0.010</u> [0.25]	H <u>±0.010</u> [0.25]	K <u>±0.005</u> [0.13]	M <u>±0.010</u> [0.25]
	8W2M	<u>1.213</u> [30.81]		<u>0.666</u> [16.92]	<u>0.984</u> [24.99]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
'	8W2S	1.213 [30.81]	<u>0.643</u> [16.33]		<u>0.984</u> [24.99]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>0.759</u> [19.28]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
	19W1M	1.541 [39.14]		<u>0.994</u> [25.25]	1.312 [33.32]		<u>0.329</u> [8.36]	<u>0.494</u> [12.55]	1.083 [27.51]	<u>0.422</u> [10.72]	<u>0.233</u> [5.92]	<u>0.422</u> [10.72]
2	19W1S	1.541 [39.14]	0.971 [24.66]		1.312 [33.32]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	1.083 [27.51]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]
4	45W2S	2.729 [69.32]	<u>2.159</u> [54.84]		<u>2.500</u> [63.50]	<u>0.311</u> [7.90]		<u>0.494</u> [12.55]	<u>2.272</u> [57.71]	<u>0.422</u> [10.72]	<u>0.243</u> [6.17]	<u>0.429</u> [10.90]



ORDERING INFORMATION - CODE NUMBERING SYSTEM

Specify Complete Connector By Selecting An Option From Step 1 Through 8

STEP	1	2	3	4	5	6	7	8	9	10
EXAMPLE	CBCD	8W2	S	0	0	0	0	S	/AA	14
STEP 1 - BASIC SECBCD Series	STEP 1 - BASIC SERIES									** STEP 10 - SPECIAL OPTIONS FOR SPECIAL OPTIONS, SEE SPECIAL OPTIONS APPENDIX ON PAGE 81.
STEP 2 - CONNECTOR Shell Size 1 - 8W2 Shell Size 2 - 19W1 *1 Shell Size 4 - 45W2	OR VARI	ANTS							/AA	P 9 - ENVIRONMENTAL DMPLIANCE OPTIONS - RoHS Compliant E: If compliance to environmental ation is not required, this step will not be
M - Male S - Female - PosiBand C	losed Entry	Signal Co						0 *5 S X	P8-SI - Zinc F - Stainle - Tin Pla	ess Steel, passivated. ated.
0 - Connector ordere power, thermocol contacts separate part numbers. 1 - Signal contacts, 2 **211 - Signal contacts, 2 with MC/FC 4012 **212 - Signal contacts, 2 with MC/FC 4016 **213 - Signal contacts, 2 with MCC/FCC 4* **214 - Signal contacts, 2: with MCC/FCC 4*	d without of uple, shield ly. See page 2 AWG-30 2 AWG-30 D power of 2 AWG-30 101D shield 2 AWG-30 4 AW	contacts. Ced, high volume (Ced, high volume (Ce	Order signa obltage or a for contact 03mm²-0.0 03mm²-0.0 03mm²-0.0 03mm²-0.0 sts. 3mm²-0.0	air et 05mm²]. 05mm²] 05mm²]			0 - V3 - V5 - VL - T - T6 - E - E2 - E3 -	EP 7 - None Lock Lock Lock Fixed Fixed Fixed Rotati Rotati	- Tin Plant LOCKI Tab, cor Tab, cor Lever, us Female Female and male and mang Male ing Male ing Male	NG AND POLARIZING SYSTEMS Innector front panel mounted. Innector rear pan
**STEP 5 - MOUNTII 0 - Mounting Hole, 0.1 02 - Mounting Hole, 0.1 F - Float Mounts, Unive S2 - Swaged Spacer, 4- S5 - Swaged Locknut, 4	20 [3.05] Ø 54 [3.91] Ø ersal 40 Thread	-)) s, 0.125 [3	3.18] Leng	th		A A	STEP 6 0 - Nor AN - Ligh AC - Ligh H - Hoo G - Hoo Z - Hoo	- HOO ne ntweight a	DS ANI Aluminun Aluminun Dpening, RFI, Die Cor Side C	D PUSH-ON FASTENERS n Hood, nickel finish. n Hood, no finish. Metal

- *145W2 variant currently available in female only.
- *2 Available on 19W1 and 45W2 connectors only.
- *3 For additional information on accessories listed in steps 5, 6, 7 and 10, see Accessory Catalog.
- *4When using G hood with CBCD variants, use the extended height hood. See Accessories Catalog for extended G hood options.
- *5 For stainless steel dimpled male versions, contact Technical Sales.

For crimping information and crimp tools, see Application Tools section, page 82.

connectpositronic com

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO VERTICALLY STACKED STANDARD DENSITY PCB MOUNT


Combo-D D-Sub

Size 20 Signal Contacts Size 8 Power Contacts

UL Recognized File #E49351

CSA Recognized File #LR54219

Telecommunication UL File #14095



The Combo-Dual Port connector series offers several combinations of power and signal contacts within the same connector assembly. Seventeen different combinations of power and signal contact stacked assemblies are available within four standard shell sizes. The connector assembly can be partially populated with either signal or power contacts installed in the connector bodies to customer selected contact positions. The stacked connectors may be spaced apart to two dimensional spacings.

On special order, the right angle (90°) printed board mount contacts may be replaced with size 8 power,

shielded or high voltage contacts having crimp or solder cup terminations. Signal contacts remain in dual port configuration.

Mounting angle brackets can be ordered riveted to the connector by specifying R2, R6, R7 and R8 options. Locking systems are available utilizing 4-40 threaded jackscrew systems, polarized or non-polarized, or with a quick-release vibration lock system for rear panel mounted connectors.

Combo-Dual Port series connectors comply with the dimensional requirements of IEC 60807-2 and DSCC 85039.

TECHNICAL CHARACTERISTICS

MATERIALS AND FINISHES:

Insulator: Glass filled polyester per ASTM D 5927 UL

94, blue color, and composite.

Contacts: Precision machined copper alloy.

Contact Plating:

Gold flash over nickel plate. Other finishes SIGNAL:

available upon request.

POWER: Gold flash over nickel. Other finishes

available upon request.

Shells: Steel with tin plate; zinc platel; stainless

steel passivated. Other materials and

finishes available upon request.

Mounting Spacers Nylon; polyester; copper alloy or steel with and Brackets: zinc plate or tin plate; phosphor bronze

with tin plate; stainless steel, passivated.

Cross Bar Nylon, UL 94V-0, black color. Push-On Fasteners: Beryllium copper, tin plated.

Jackscrew Systems: Brass or steel with zinc plate or clear zinc plate or tin plate; stainless steel,

passivated.

Lock tabs, steel with nickel plate. Vibration Lock Systems:

Non-magnetic versions are available, contact Technical Sales.

MECHANICAL CHARACTERISTICS:

Signal Contacts: Size 20 contacts, male - 0.040 inch

> [1.02mm] mating diameter. Female contact - rugged open entry. PosiBand closed entry female options are also

available.

Contact Retention

In Insulator: 9 lbs. [40N]

Contact Terminations: Printed board mount with right angle

> (90°) terminations supported by alignment bar. Termination diameter

0.028 inch [0.71mm].

Power Contacts: Size 8 contact, male - 0.142 inch

[3.61mm] mating diameter.

MECHANICAL CHARACTERISTICS, continued:

Contact Retention

In Insulator: 22 lbs. [98N]

Contact Terminations: Printed board mount with right angle

(90°) terminations of 0.078 inch [1.98mm]

diameter.

Combo-D D-Sub

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO VERTICALLY STACKED STANDARD DENSITY PCB MOUNT



TECHNICAL CHARACTERISTICS, continued

continued from previous page. . . .

Shells: Male connector shells may be dimpled for

EMI/ESD ground paths.

Polarization: Trapezoidally shaped shells and polarized

jackscrews.

Mounting BracketRiveted fasteners with 0.120 inchRiveted to Connector:[3.05mm] diameter clearance hole, with

4-40 threads or 4-40 threads with nylon

lock insert.

Mounting To

Printed Board: Rapid installation push-on fasteners.

Locking Systems: Jackscrews and vibration locking system

for either front or rear panel mounted

connectors.

Mechanical Operations: 500 operations minimum per IEC 60512-

5.

SIZE 8 CONTACTS

POWER CONTACTS

Electrical characteristics for 0.078 inch diameter terminations,

see page 4.

CONNECTOR

Insulation Resistance: 5 G ohms.

Clearance and Creepage

Distance (minimum): 0.039 inch [1.0mm] **Working Voltage:** 300 V r.m.s.

CLIMATIC CHARACTERISTICS:

Temperature Range: -55°C to +125°C.

Damp Heat, Steady State: 10 days.

ELECTRICAL CHARACTERISTICS:

SIZE 20 CONTACTS


Contact Current Rating: 7.5 amperes nominal.

Initial Contact Resistance: 0.008 ohms maximum.

Proof Voltage: 1000 V r.m.s.

CONTACT VARIANTS

FACE VIEW OF MALE OR REAR VIEW OF FEMALE



Notes:


- *12WK2 connectors have 1 male and 1 female contacts. Female connector should be loaded with female contact in A2 position.
- *23WK3 male variant contains 2 male contacts and 1 female contact. Female variant contains 2 female contacts and 1 male contact

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO VERTICALLY STACKED STANDARD DENSITY PCB MOUNT

Combo-D D-Sub

RIGHT ANGLE (90°) PRINTED BOARD MOUNT CONNECTOR 4 ROW CONNECTOR UNIT, 0.283 [7.19] CONTACT EXTENSION

See temperature rise curves on pages 1 and 2



NOTE:

30 ampere 0.125 [3.18] Ø power contacts may be ordered at special request for a limited number of CBDP variants. Contact technical sales for details.

CONNECTOR DESIGNATION	С	C D			
СВДРВ	<u>0.750</u>	<u>1.244</u>	<u>0.256</u>		
	[19.05]	[31.60]	[6.50]		
CBDPC	<u>0.900</u>	<u>1.394</u>	<u>0.406</u>		
	[22.86]	[35.41]	[10.31]		

CONNECTOR VARIANT	A	В
SHELL SIZE 1	<u>1.213</u> [30.81]	<u>0.984</u> [24.99]
SHELL SIZE 2	<u>1.541</u> [39.14]	<u>1.312</u> [33.32]
SHELL SIZE 3	<u>2.088</u> [53.04]	<u>1.852</u> [47.04]
SHELL SIZE 4	<u>2.729</u> [69.32]	<u>2.500</u> [63.50]

Note: Printed board power contacts (size 8) may be replaced with a size 8 removable power, shielded, air or high voltage contact having solder or crimp terminations.


PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO VERTICALLY STACKED STANDARD DENSITY PCB MOUNT



RIGHT ANGLE (90°) PRINTED BOARD CONTACT HOLE PATTERN

HOLE IDENTIFICATION SHOWN IS FOR FEMALE CONNECTOR OVER MALE CONNECTOR.

MOUNT CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROW.



SUGGESTED PRINTED BOARD HOLE SIZES:

Suggest 0.045 [1.14] Ø hole for signal contact termination positions.

Suggest 0.098 [2.49] Ø hole for 0.078 [1.98] Ø power contact termination positions.

Suggest 0.123 ±0.003 [3.12] Ø hole for mounting connector with push-on fasteners.

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO VERTICALLY STACKED STANDARD DENSITY PCB MOUNT

Combo-D D-Sub

0.109 [2.77]

-0.893 [22.68]


-1.250 [31.75]

27W2/27W2

RIGHT ANGLE (90°) PRINTED BOARD CONTACT HOLE PATTERN

HOLE IDENTIFICATION SHOWN IS FOR FEMALE CONNECTOR OVER MALE CONNECTOR.

MOUNT CONNECTOR WITH MATING FACE POSITIONED TO FOLLOW DIRECTION OF ARROW.



0.013

[0.33]

SUGGESTED PRINTED BOARD HOLE SIZES:

0.618 [15.70]

-0.893 [22.68]

-1.250 [31.75]

Suggest 0.045 [1.14] Ø hole for signal contact termination positions.

Suggest 0.098 [2.49] Ø hole for 0.078 [1.98] Ø power contact termination positions.

Suggest 0.123 ±0.003 [3.12] Ø hole for mounting connector with push-on fasteners.

25W3/25W3

Mounting holes must move 0.020 [0.51] ± 0.010 opposite direction of arrow for use of unriveted mounting bracket with connectors.

0.013

[0.33]

Combo-D D-Sub

PROFESSIONAL, INDUSTRIAL AND MILITARY QUALITY THREE PERFORMANCE LEVELS FOR BEST COST/PERFORMANCE RATIO VERTICALLY STACKED STANDARD DENSITY PCB MOUNT



ORDERING INFORMATION - CODE NUMBERING SYSTEM

Specify Complete Connector By Selecting An Option From Step 1 Through 8

STEP	1	2	3	4
EXAMPLE	CBDPB	9W4	F	N7T
UPPER CONNECTOR				
STEP 1 - BASIC SEF CBDPB Series CBDPC Series	RIES			
STEP 2 - CONNECT	OR VARIA	NTS		
Shell Size 1 2WK2, 5W1				
Shell Size 2 3W3, 3WK3, 7W2, 11W1	l			
Shell Size 3 5W5, 9W4, 13W3, 17W2	2, 21W1			
Shell Size 4 BW8, 13W6, 17W5, 21W	/A4, 25W3,	27W2		
STEP 3 - CONNECTO	R GENDE	R		
- Female - Professional Open Entry S M - Male		cts		
พ - เพลเอ S - Female - Industrial / M PosiBand Clo			itacts	

STEP 4 - LOCKING, POLARIZING, MOUNTING AND PUSH-ON FASTENER SYSTEMS

- 0 None
- R2 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Thread, Fixed Female Jackscrews and Cross Bar
- R6 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 0.120 [3.05] Ø Mounting Hole with Cross Bar
- R7 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Threads with Cross Bar
- R8 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Locknut with Cross Bar
- N2 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Thread, Fixed Female Jackscrews with Cross Bar and Push-On Fastener
- N6 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 0.120 [3.05] Ø Mounting Hole with Cross Bar and Push-on Fastener
- N7 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Threads with Cross Bar and Push-on Fastener
- N8 Bracket, Mounting, Right Angle (90°) Metal, Swaged to Connector with 4-40 Locknut with Cross Bar and Push-on Fastener
- V3 Lock Tab.
- V5 Lock Tab, connector rear panel mounted.
- Fixed Female Jackscrews
- T2 Fixed Female Jackscrews
- T6 Fixed Male and Female Polarized Jackscrews

,			-		-	
,	5	6	7	8	9	10
/	9W4	F	N7T	0	/AA	14
	OPTI THE FOF CON STE	ONS AF SAME A UPPER NECTO EPS 2, 3 AND 4	RE AS R	0 - *2 S - X -	/AA NOTE legisla used. P 8 - SI Zinc Pla Stainles Tin Plat	s Steel, passivated.

NOTE

- *1 Contacts can be supplied with Military contact plating, see page 81.
- *2 For stainless steel dimpled male versions, contact Technical Sales.

For crimping information and crimp tools, see Application Tools section, page 82.

NOTE: Size 8 removable power contacts with solder or crimp terminations with power ratings of 10, 20 and 40 amperes may be ordered in lieu of the right angle (90°) board mounted power contact. Removable size 8 shielded, air and high voltage contacts may also be ordered separately in lieu of the power contact. See pages 68-80 for contact part numbers.












COMBO-D CONNECTOR SAVERS GENDER CHANGERS

Combo-D D-Sub

Professional Quality Connectors
ACBDP Series
Size 20 "Open Entry" or
PosiBand® "Closed Entry"
Contact Design

Industrial /Military Quality Connectors
- ACBMP Series
Size 20 PosiBand®
"Closed Entry" Contact Design

Connector Saver



ACBDP and ACBMP series connectors are suitable for use in any applications requiring high performance characteristic. The normal density ACBDP and ACBMP series are available in standard Combo-D connector variants.

ACBDP and ACBMP series connectors utilize precision machined contacts for strength and durability. The ACBDP female contact features a rugged "Open Entry" design or PosiBand "Closed Entry" design for even higher reliability. ACBMP connectors features PosiBand "Closed Entry" contacts and military contact plating.

ACBDP and ACBMP series connectors can be mated to a connector which would normally experience high numbers of mating cycles. The ACBDP/ACBMP connector can be easily replaced, "Saving" a connector which is not easily replaced.

These connectors can also be used as a "gender changer". Connector Savers are also available in standard and high density D-subminiature versions, please consult our Professional, Industrial and Military Performance D-subminiature Connectors catalog for more information.

For high density 8W2, 19W1 and 45W2 adapter variants contact Technical Sales.

TECHNICAL CHARACTERISTICS

MATERIALS AND FINISHES:

Insulator: Glass filled polyester per ASTM D 5927

UL 94V-0, blue color.

SIGNAL CONTACTS:

ACBDP Series: Precision machined high tensile copper alloy

open entry design.

ACBMP Series: Precision machined copper alloy PosiBand

closed entry design.

POWER CONTACTS: Precision machined copper alloy closed entry

design.

Contact Plating:

ACBDP Series: Gold flash over nickel plate.

 $\begin{array}{ll} \textbf{ACBMP Series:} & 0.000050 \ [1.27\mu] \ gold \ over \ nickel \ plate. \\ \textbf{Shells:} & Steel \ with \ tin \ plate; \ zinc \ plate; \ stainless \ steel \end{array}$

passivated. Other materials and finishes

available upon request.

Jackscrew Systems:

Brass or steel with zinc plate clear zinc plate or

tin plate; stainless steel, passivated.

Non-magnetic versions are available, contact Technical Sales.

MECHANICAL CHARACTERISTICS:

FIXED CONTACTS:

SIGNAL CONTACTS: Size 20 contacts, male - 0.040 inch [1.02 mm]

diameter. ACBDP series has female open entry contact or PosiBand closed entry contacts

optional, see page 69 for details.

ACBMP series offer female PosiBand closed

ntry contacts.

POWER CONTACTS: Size 8 contacts, male - 0.142 inch [3.61 mm]

diameter. Female contact features Large Surface Area (L.S.A.) closed entry contact design utilizing BeCu mechanical retention

member.

continued from previous page. . . .

MECHANICAL CHARACTERISTICS, continued:

Connector Saver: Male to female or male to male.

Contact Retention:

Signal: 9 lbs. [40 N]. Power: 22 lbs. [98 N].

Shells: Male shells may be dimpled for

EMI/ESD ground paths.

Polarization: Trapezoidally shaped shells.

Mechanical Operations:

ACBDP Series: 500 operations, minimum, per IEC

60512-5.

ACBMP Series: 1,000 operations, minimum, per IEC 60512-5.

ELECTRICAL CHARACTERISTICS:

SIZE 20 CONTACTS

Contact Current Rating: 7.5 amperes, nominal. Initial Contact Resistance: 0.008 ohms, maximum. Proof Voltage: 1,000 V r.m.s.

SIZE 8 CONTACTS

POWER CONTACTS

Contact Current Rating: 70 amperes, per UL 1977.

See Temperature Rise Curves on pages 1-2.

Initial Contact Resistance: 0.0005 ohms, maximum

Proof Voltage: 1,000 V r.m.s.

CONNECTOR

Insulation Resistance: 5 G ohms.

Clearance and

Creepage Distance: 0.039 inch [1.0 mm], minimum.

Working Voltage: 300 V r.m.s.


CLIMATIC CHARACTERISTICS:

Temperature Range: -55°C to +125°C.

ACBDP/ACBMP SERIES SIZE 20 AND SIZE 8 CONTACT CONNECTOR SAVER

CONTACT VARIANTS

FACE VIEW OF MALE OR REAR VIEW OF FEMALE





Note: For high density 8W2, 19W1 and 45W2 variants contact Technical Sales for availability.



COMBO-D CONNECTOR SAVERS GENDER CHANGERS


STANDARD SHELL ASSEMBLY DIMENSIONS SIZE 20 AND SIZE 8 CONTACTS CODE 0 AND S





CONNECTOR	A	B	B1	C	D	D1	E	K1
SIZE	±0.015	±0.005	±0.005	±0.005	±0.005	±0.005	±0.015	±0.005
SHELL SIZE 1	1.213	<u>0.643</u>	<u>0.666</u>	<u>0.984</u>	<u>0.311</u>	0.329	<u>0.494</u>	<u>0.233</u>
	[30.81]	[16.33]	[16.92]	[24.99]	[7.90]	[8.36]	[12.55]	[5.92]
SHELL SIZE 2	1.541	<u>0.971</u>	<u>0.994</u>	1.312	<u>0.311</u>	<u>0.329</u>	<u>0.494</u>	<u>0.233</u>
	[39.14]	[24.66]	[25.25]	[33.32]	[7.90]	[8.36]	[12.55]	[5.92]
SHELL SIZE 3	2.088	1.511	1.534	1.852	<u>0.311</u>	0.329	<u>0.494</u>	<u>0.230</u>
	[53.04]	[38.38]	[38.96]	[47.04]	[7.90]	[8.36]	[12.55]	[5.84]
SHELL SIZE 4	2.729	2.159	2.182	2.500	<u>0.311</u>	0.329	<u>0.494</u>	<u>0.230</u>
	[69.32]	[54.84]	[55.42]	[63.50]	[7.90]	[8.36]	[12.55]	[5.84]
SHELL SIZE 5	2.635	2.064	2.079	2.406	<u>0.423</u>	<u>0.441</u>	<u>0.605</u>	<u>0.230</u>
	[66.93]	[52.43]	[52.81]	[61.11]	[10.74]	[11.20]	[15.37]	[5.84]
SHELL SIZE 6	2.729	2.189	2.212	2.500	<u>0.485</u>	<u>0.503</u>	<u>0.668</u>	<u>0.230</u>
	[69.32]	[55.60]	[56.18]	[63.50]	[12.32]	[12.78]	[16.97]	[5.84]

JACKSCREW SYSTEMS CODE E, E6, T AND T6





ORDERING INFORMATION - CODE NUMBERING SYSTEM

Specify Complete Connector By Selecting An Option From Step 1 Through 9

	•				-		-			•	-		
STEP	1	2	3	4	5	6	7	8	9	10	11		
EXAMPLE	ACBDP	11W1	F	S	Х	11W1	M	S	Х	/AA	-14		
STEP 1 - BASIC: ACBDP - Professional Industrial Quality, see ACBMP - Military corwith "closed entry" for nal contacts plated ([1.27µ] gold over nice Choose "S" or "M" in STEP 2 - CONNES Shell Size 1 (Sw1) Shell Size 2 (3w3, 7w2, 11w1) Shell Size 3 (5w5, 9w4, 13w3, 17) Shell Size 4 (8w8, 13w6, 17w5, 2) Shell Size 5 (24w7, 36w4, 43w2, Shell Size 6 (46w4) Note: For high demand 45w2 variate Technical Sales 1 (5w1) STEP 3 - 1ST COE F - Female - Profession (5w2) Female - Industing Industrial Sales 1 (5w2) Female -	SERIES al / e Step 3. Informance emale sig- 0.000050 kel plate. In Step 3. ICTOR VA W2, 21W1 INWA4, 25W 47W1 Insity 8W2, 19 Inst sontact for availability INNECTO Sisional Level Entry Signal rial / Military	RIANT 3, 27W2 W1 by. R GENI Contacts Level -	DER	S	X	11W1	M	*2 5 ************************************	STEP 0 - **S - X - Z - TEP 8 - 0 - Swac S - Swac E - Rotat (Selec 6 - Rotat (Selec	STEP 11 - SPECIAL OPTIONS, SEI SPECIAL OPTIONS, SEI SPECIAL OPTIONS APPEND ON PAGE 81. STEP 10 - ENVIRONMENTAL COMPLIANCE OPTION (AA - RoHS Compliant) NOTE: If compliance to environmental legislation is not required, this step will not be used. Example: ACBDP11W1FSX11W1MSX 9 - 2ND CONNECTOR SHELL OP Zinc Plated. Stainless Steel, passivated. Tin Plated and Dimpled (male connectors only 12 Plated and Dimpled (male connectors only 12 Plated and Dimpled (male connectors only 13 Spacer 4-40 UNC-2B threads ing male and female jackscrews ct 0 in Step 4) ing male and female polarized jackscrew ct 0 in Step 4)			
PosiBa	and Closed E cts. Military (Entry Sign							(Seled 6 - Fixed	ct 0 in St	d female polarized jackscrew		
*2 STEP 4 - 1 ST CC 0 - Swaged spa S - Swaged spa *3 E - Rotating mal	cer 0.120 [3 cer 4-40 UN e and femal	3.05µ] mc NC-2B thi	ounting h reads					EP 7 - 2 Male	ND COI	NNECT	OR GENDER		
(Select 0 ii *3 E6 - Rotating mal (Select 0 in S *3 T - Fixed male a (Select 0 in S	e and femal Step 8) nd female ja Step 8)	ackscrew	'S					- 2 ND CO variant a					
*3T6 - Fixed male a		ioiarized j	jackscre\	N									

STEP 5 - 1ST CONNECTOR SHELL OPTION

- 0 Zinc Plated.
- *4S Stainless Steel, passivated.X Tin Plated.

(Select 0 in Step 8)

- Z Tin Plated and Dimpled (male connectors only).

NOTES

- *¹Male option in Step 3 available only on connector variants 5W1, 3W3, 7W2, 11W1,17W2, 21W1, 21WA4, 27W2, 24W7, 46W4.
- \star2 Connector mating style for both connectors must be the same if 0 or S is used. If E, E6, T or T6 is used in either Step 4 or 8 the other step must be 0.
- *3 For hardware information, see page 59.
- *4 For stainless steel dimpled male versions, contact Technical Sales.
- $^{\rm \star 5}{\rm Connector}$ variant for both connectors must be the same.




Positronic Industries is **known** around the world **for offering** our customers **flexibility** when choosing connectors.

In addition to allowing **customers** to **create** part numbers for **particular applications**, Positronic offers a **wide variety** of features and accessories within our products.

Positronic is also **eager** to modify existing products **to meet unique customer requirements.** If you do not find what you need with this catalog, please **contact us** for assistance.

SEQUENTIAL MATING CONTACTS



Note: A third level can be accomplished with signal contacts where applicable.


Three levels of sequential mating are possible:


- First mate accomplished by a size 12 power contact. Male contact diameter is 0.094 inch.
- Second mate accomplished by a size 8 power contact. Male contact diameter is 0.142 inch.
- Third mate accomplished by size 20 signal contacts, as applicable.

CONTACT TECHNICAL SALES FOR MORE INFORMATION!

SIZE 8 CONTACT STABILIZATION FEATURE

MINIMIZES FLOAT IN SIZE 8 CONTACT POSITIONS






WITH STABILIZER

WITHOUT STABILIZER

CBD size 8 male contacts are removed toward the rear after utilizing front release tooling. Space must be provided between the contact and the connector molding so the tooling can slide over the mating portion of the contact. This fact allows the contact to float.

In some applications this float creates problems in alignment during mating. Many male contact CBD variants offer an integral stabilizing feature to minimize problems created by float in size 8 contacts. An alternate tool is used to remove the contact if necessary. Tool number is 4311-0-1-0.

The stabilization feature is currently available for the following male contact variants:



Add MOS -1570.4 to end of part number. Example: CBD3W3M00000-1570.4



COMBO-D CONNECTORS WITH *1100 AMP HIGH CURRENT REMOVABLE CRIMP POWER CONTACT



HIGH CONDUCTIVITY SIZE 8 CONTACTS WHICH CAN BE TERMINATED TO 6 AWG WIRE ALLOW VERY HIGH CURRENTS TO BE CARRIED THROUGH COMBO-D TYPE CONNECTORS.

TECHNICAL CHARACTERISTICS

MATERIALS AND FINISHES:

Contacts: High conductivity copper alloy.

Plating:

Standard Finish: Gold flash over nickel plate.

Optional Finishes: 30µin [.76µm] gold over nickel by adding

"-14" suffix onto part number.

Example: FC4006D-14

50µin [1.27µm] gold over nickel by adding "-15" suffix onto part number.

Example: MC4006D-14

CLIMATIC CHARACTERISTICS:

Temperature Range: -55°C to +125°C.

*1 per UL 1977 Testing

ELECTRICAL CHARACTERISTICS:

POWER CONTACTS

Contact Current Rating: See Temperature Rise Curve on

page 64.

Initial Contact Resistance: 0.0003 ohms max. per IEC 60512-2,

Test 2b.

Proof Voltage: 1900 V r.m.s. Working Voltage: 450 V r.m.s.

MECHANICAL CHARACTERISTICS:

Size 8 Removable

Contacts: Rear insertion, front release. **Durability:** 500 cycles minimum. Vibration: 20g from 10 Hz to 500 Hz.

Shock: 30g-11ms.

100 AMP HIGH CURRENT REMOVABLE CRIMP POWER CONTACT

CONTACTS USED WITH 6 AWG WIRE 6 AWG [16.0mm²] max.

*1 CONTACTS ORDERED SEPARATELY

SIZE 8

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

*2 FEMALE CONTACT

"CLOSED ENTRY" DESIGN, L.S.A.

-0.865 [21.97] 0.624 0.336 [8.53] [15.85] Ø0.233 [5.92] \bigcirc FC4006D

0.864 [21.95] 0.336 [8.53] 10 Ø0.233 [5.92] Ø0.142 [3.61] MC4006D

MALE CONTACT

*2 NOTE: Female contacts feature Large Surface Area (L.S.A.) closed entry contact design which provides maximum mating surfaces between male and female contact and reduced contact resistance during operation.

MATERIAL: High conductivity copper alloy.

STANDARD FINISH: Gold flash over nickel plate.

OPTIONAL FINISHES: 30µin [.76µm] gold over nickel by adding "-14" suffix onto


part number. Example: FC4006D-14

50µin [1.27µm] gold over nickel by adding "-15" suffix


onto part number. Example: MC4006D-15.

0

COMBO-D CONNECTORS WITH TWO CONTACT POSITIONS



CBD3W3M00000-1841.0



CBD3W3F00000-1841.0

COMBO-D CONNECTORS WITH THREE CONTACT POSITIONS



CBD5W5M00000-1841.1



CBD5W5F00000-1841.1

COMBO-D CONNECTORS WITH FOUR CONTACT POSITIONS




CBD8W8M00000-1841.2



CBD8W8F00000-1841.2

TEMPERATURE RISE CURVE




TEMPERATURE RISE (°C)

Test conducted in accordance with UL1977. All power contacts under load.


Curves were developed using CBD3W3, 5W5, and 8W8 connectors with MC/FC4006D contacts terminated with 6 AWG wire.



STRAIGHT PRINTED BOARD MOUNT HIGH VOLTAGE CONTACT SIZE 8




RIGHT ANGLE (90°) PRINTED BOARD MOUNT HIGH VOLTAGE CONTACT SIZE 8



CONTACT TECHNICAL SALES FOR MORE INFORMATION!




BUS BAR CONTACT SIZE 8 POWER CONTACT



Power contacts can be offered with terminations suitable for use with bus bars.

CONTACT TECHNICAL SALES FOR MORE INFORMATION!




CONTACT TECHNICAL SALES FOR MORE INFORMATION!



CUSTOMER SPECIFIED CONTACT TERMINATION LENGTH

Positronic can supply CB series connectors with customer specified termination lengths. We have a wide variety of options available.


STRAIGHT PRINTED BOARD MOUNT



*Note:

PCB spacer height can be adjusted according to contact termination length

RIGHT ANGLE (90°) PRINTED BOARD MOUNT



X and Y contact termination lengths can be custom designed to fit your application requirements.

CONTACT TECHNICAL SALES FOR MORE INFORMATION!

Connectors Designed To Customer Specifications

Positronic Combo-D connectors can be modified to customers specifications.

Examples: select loading of contacts for cost savings or to gain creepage and clearance distances; longer PCB terminations; customer specified hardware; sealing for water resistance.

Contact Technical Sales with your particular requirements.



REMOVABLE CONTACT TECHNICAL CHARACTERISTICS

SIZE 22 REMOVABLE CONTACT

MATERIALS AND FINISHES:

Precision machined copper alloy with gold flash over nickel. Other finishes are available, see pages 69 and 81 for optional finishes.

MECHANICAL CHARACTERISTICS:

Insert contact to rear face of insulator, release from rear face of insulator. Size 22 contacts, 0.030 inch [0.76 mm] mating diameter male contacts. Female PosiBand closed entry contact design. Terminations for 20, 22, 24, 26, 28, and 30 AWG. Closed barrel crimp.

ELECTRICAL CHARACTERISTICS:

Contact Current Rating: 5 amperes nominal. Initial Contact Resistance: 0.010 ohms maximum.

THERMOCOUPLE CONTACTS:

Straight and right angle (90°) PCB mount contacts are available, contact Technical Sales for details.

Size 22 crimp contacts are available, see page 71 for details.

SIZE 20 REMOVABLE CONTACT

MATERIALS AND FINISHES:

Precision machined copper alloy with gold flash over nickel. Other finishes are available, see pages 69 and 81 for optional finishes.

MECHANICAL CHARACTERISTICS:

Insert contact to rear face of insulator, release from rear face of insulator. Size 20 contacts, 0.040 inch [1.02 mm] mating diameter male contacts. Female PosiBand closed entry or rugged open entry contact design.

ELECTRICAL CHARACTERISTICS:

Contact Current Rating: 7.5 amperes nominal.

0.008 ohms max. per IEC 60512-2, **Initial Contact Resistance:**

THERMOCOUPLE CONTACTS:

Straight and right angle (90°) PCB mount contacts are available, contact Technical Sales for details.

Size 20 crimp contacts are available, see page 74 for details.

SIZE 16 REMOVABLE CONTACT

MATERIALS AND FINISHES:

STANDARD: Precision machined copper alloy with gold

flash over nickel. Other finishes are available, see pages 69 and 81 for optional finishes.

HIGH CONDUCTIVITY: High conductivity copper alloy, gold flash

over nickel. Other finishes are available, see pages 69 and 81 for optional finishes.

MECHANICAL CHARACTERISTICS:

STANDARD AND

HIGH CONDUCTIVITY: Insert contact to rear face of insulator,

release from front face of insulator. Size 16 contacts, 0.0625 inch [1.588mm] mating

ELECTRICAL CHARACTERISTICS:

Contact Current Rating - Tested per UL 1977:

Standard Contact Material: 28 amperes. **High Conductivity Contact Material:** 40 amperes.

See Temperature Rise Curves on page 2 for details.

Initial Contact Resistance:

0.0016 ohms max. Per IEC 60512-Standard Contact Material:

2, Test 2b.

diameter male contacts. Female PosiBand closed entry contact design. Terminations for

12, 14, 16, 18, 20, 22, 24, 26, and 28 AWG.

High Conductivity

Contact Material: 0.001 ohms max. Per IEC 60512-2,

Test 2b.

SIZE 8 REMOVABLE CONTACT

MATERIALS AND FINISHES:

Precision machined copper alloy with gold STANDARD:

flash over nickel. Other finishes are available, see pages 69 and 81 for optional finishes.

HIGH CONDUCTIVITY: High conductivity copper alloy, gold flash

over nickel. Other finishes are available, see pages 69 and 81 for optional finishes.

HIGH VOLTAGE:

PTFE teflon Insulator Material:

Precision machined copper alloy with Contacts:

0.000030 inch [0.76µ] gold over nickel. Other finishes are available, see pages 69 and 81

for optional finishes.

SHIELDED:

Dielectric Material: PTFE teflon

Inner Contacts: Precision machined copper alloy with

0.000030 inch [0.76µ] gold over nickel. Other finishes are available, see pages 69 and 81

for optional finishes.

Precision machined copper alloy with gold **Outer Contacts:**

flash over nickel. Other finishes are available, see pages 69 and 81 for optional finishes.

AIR LINE COUPLER: Stainless steel, see page 80.

MECHANICAL CHARACTERISTICS:

STANDARD AND

HIGH CONDUCTIVITY: Insert contact to rear face of insulator,

release from front face of insulator. Size 8 contacts, 0.142 inch [3.61 mm] mating diameter male contacts, closed entry

female contacts

HIGH VOLTAGE: Insert contact to rear face of insulator,

release from front face of insulator. Size 8 contacts. Straight and right angle (90°) terminations. 0.041 inch [1.04 mm] minimum

hole diameter.

Durability: 500 cycles minimum. Vibration: 20g from 10 Hz to 500 Hz.

Shock: 30g-11ms.

. . . continued on next page

REMOVABLE CONTACT TECHNICAL CHARACTERISTICS

continued from previous page . . .

MECHANICAL CHARACTERISTICS, continued:

SHIELDED: Insert contact to rear face of insulator.

release from front face of insulator. Size 8 contacts. See page 78 table of cable sizes for contact termination dimensions.

Durability: 500 cycles minimum. Vibration: 20g from 10 Hz to 500 Hz.

Shock: 30g-11ms.

AIR LINE COUPLER: Insert contact to rear face of insulator,

release from front face of insulator.

ELECTRICAL CHARACTERISTICS:

POWER CONTACTS:

For electrical characteristics, see page 4.

HIGH VOLTAGE:

Flash over Voltage: 3600 V r.m.s. 2700 V r.m.s. Proof Voltage:

Initial Contact Resistance: 0.008 ohms maximum.

SHIELDED:

Initial Contact Resistance: 0.008 ohms maximum. Nominal Impedance: 50 ohms. -0.46 dB at 1 GHz Insertion Loss:

-1.5 dB at 2 GHz VSWR-1.15 average at 1 GHz 1.56 average at 2 GHz

Above values measured using frequency domain techniques. Proof Voltage: 1000 V r.m.s.

OPTIONAL PLATING FINISHES

30µin [.76µm] gold over nickel by adding

"-14" suffix onto part number. Example:

FC120N4-14.

-15 50µin [1.27µm] gold over nickel by adding

"-15". Example: FC120N4-15.


RoHS OPTIONS:

/AA Environmental Compliance Option:

RoHS compliant can be achieved by adding "/AA" suffix onto part number. Examples: FC120N4/AA or for optional finishes use FC120N4/AA-14.

What makes Positronic's PosiBand® contact interface significant?





- Higher reliability in harsh environments and repeated mating cycles.
- PosiBand crimp contacts do not need to be annealed. Split tine D-subminiature contacts are commonly annealed at the crimp barrel, with the possibility of reliability problems at the contact interface if the annealing is performed incorrectly.
- Electrical and mechanical function of the contact interface are separated since the PosiBand contact is a two-piece design. Contact normal force is provided by the "Posiband spring member", which allows higher mechanical reliability. The

electrical continuity path is supported through the base contact, which allows a greater number of electrical paths on a "micro" level when compared to split tine contact design.

- Higher reliability at prices comparable to the "split tine" design.
- PosiBand is protected by US Patent 7,115,002.

For a detailed white paper visit: www.connectpositronic.com/posiband



REMOVABLE CRIMP SIGNAL CONTACT

FOR USE WITH CBCD SERIES CONNECTORS

SIZE 22 **QUALIFIED TO AS39029**

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

*MILITARY **SPECIFICATION CONTACTS**

STANDARD FINISH:


per AS39029 specifications

COLOR CODE:

MALE CONTACT: ORANGE/BLUE/BLACK

FEMALE CONTACT:

ORANGE/GREEN/YELLOW



FEMALE PART NUMBER	WIRE SIZE AWG [mm²]	
*M39029/57-354	22 / 24 / 26 / 28 [0.3/0.25/0.12/0.08]	
0		

Positronic is qualified to supply the legacy design, as well as, the PosiBand design. If the requirement is for the PosiBand design exclusively, notify sales at time of quotation for order placement when requesting M39029 contacts.

MALE	WIRE SIZE	
PART NUMBER	AWG [mm²]	
*M39029/58-360	22 / 24 / 26 / 28 [0.3/0.25/0.12/0.08]	

REMOVABLE CRIMP SIGNAL CONTACT

FOR USE WITH CBCD SERIES CONNECTORS


SIZE 22




Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

FEMALE CONTACT

"CLOSED ENTRY" DESIGN



MALE CONTACT



FEMALE	WIRE SIZE
PART NUMBER	AWG [mm²]
FC8022D2	22 / 24 / 26 / 28 / 30 [0.3/0.25/0.12/0.08/0.05]

MALE	WIRE SIZE	
PART NUMBER	AWG [mm²]	
MC8022D	22 / 24 / 26 / 28 / 30 [0.3/0.25/0.12/0.08/0.05]	

CRIMP SIGNAL CONTACT

FOR USE WITH CBCD SERIES CONNECTORS

CONTACTS USED WITH 20 AWG WIRE

SIZE 22


The crimp area of these contacts is not protected when fully seated in the connector molding. These contacts require shrink tubing after installation. These contact cannot be removed from connector after installation. Not suitable for fully loaded connector.



all applicable crimp contacts, contact Technical Sales for

connector part number.

Authentic Positronic



Crimp area extends above connector molding.

FEMALE	WIRE SIZE
PART NUMBER	AWG [mm²]
FC8020D2	20 [0.5] max

MALE	WIRE SIZE
PART NUMBER	AWG [mm²]
MC8020D	20 [0.5] max

REMOVABLE THERMOCOUPLE SIGNAL CRIMP SIGNAL CONTACT

FOR USE WITH CBCD SERIES CONNECTORS


SIZE 22

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.



FEMALE CONTACT "CLOSED ENTRY" DESIGN -0.520 [13.21] -Ø0.047 [1.19] Color Code Ø0.035 -0.150 [3.81]

MALE CONTACT



TYPE	MATERIAL	FEMALE PART NUMBER	MALE PART NUMBER	COLOR CODE*	WIRE SIZE AWG [mm²]
К	CHROMEL (+)	FC8022D2CH	MC8022DCH	WHITE	<u>22 / 24 / 26</u> [0.3 / 0.25 / 0.12]
	ALUMEL (-)	FC8022D2AL	MC8022DAL	GREEN	<u>22 / 24 / 26</u> [0.3 / 0.25 / 0.12]
т	COPPER (+) with gold flash	FC8022D2CU	MC8022DCU	RED	<u>22 / 24 / 26</u> [0.3 / 0.25 / 0.12]
-	CONSTANTAN (-)	FC8022D2CO	MC8022DCO	YELLOW	<u>22 / 24 / 26</u> [0.3 / 0.25 / 0.12]
Е	CHROMEL (+)	FC8022D2CH	MC8022DCH	WHITE	<u>22 / 24 / 26</u> [0.3 / 0.25 / 0.12]
	CONSTANTAN (-)	FC8022D2CO	MC8022DCO	YELLOW	<u>22 / 24 / 26</u> [0.3 / 0.25 / 0.12]

[0.89]

For more information on the availability of Type J thermocouple contacts, please contact Technical Sales.

For more information about thermocouple contacts with PCB solder termination, please contact Technical Sales.

Chromel® and Alumel® are registered trademarks of Hoskins Manufacturing Company



MILITARY LEVEL REMOVABLE CRIMP SIGNAL CONTACT

FOR USE WITH CBC SERIES CONNECTORS

Authentic Positronic These contacts utilize authentic Positronic PosiBand^o technology Protected by U.S. Patent 7,115,002

SIZE 20 **QUALIFIED TO AS39029**

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

*MILITARY **SPECIFICATION CONTACTS**

STANDARD FINISH:

50µin [1.27µm] gold over nickel


COLOR CODE:

MALE CONTACT:

ORANGE/BLUE/WHITE FEMALE CONTACT: ORANGE/BLUE/GRAY

FEMALE CONTACT


"CLOSED ENTRY" DESIGN



FEMALE	WIRE SIZE	
PART NUMBER	AWG [mm²]	
*M39029/63-368	<u>20 / 22 / 24</u> [0.5/0.3/0.25]	

Positronic is qualified to supply the legacy design, as well as, the PosiBand design. If the requirement is for the PosiBand design exclusively, notify sales at time of quotation for order placement when requesting M39029 contacts.

MALE CONTACT



MALE	WIRE SIZE
PART NUMBER	AWG [mm²]
*M39029/64-369	<u>20 / 22 / 24</u> [0.5/0.3/0.25]

INDUSTRIAL / MILITARY LEVEL REMOVABLE CRIMP SIGNAL CONTACT

FOR USE WITH CBC SERIES CONNECTORS


SIZE 20

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.




FEMALE CONTACT

"CLOSED ENTRY" DESIGN



FEMALE PART NUMBER	WIRE SIZE AWG [mm²]	ØA
FC6020D2	<u>20 / 22 / 24</u> [0.5/0.3/0.25]	<u>0.045</u> [1.14]
FC6026D2	<u>26 / 28 / 30</u> [0.12/0.08/0.05]	<u>0.027</u> [0.69]

MALE CONTACT



MALE PART NUMBER	WIRE SIZE AWG [mm²]	ØA
MC6020D	<u>20 / 22 / 24</u> [0.5/0.3/0.25]	<u>0.045</u> [1.14]
MC6026D	<u>26 / 28 / 30</u> [0.12/0.08/0.05]	<u>0.027</u> [0.69]



INDUSTRIAL / MILITARY LEVEL CRIMP SIGNAL CONTACT

FOR USE WITH CBC SERIES CONNECTORS
CONTACTS USED WITH 18 AWG WIRE

SIZE 20




The crimp area of these contacts is not protected when fully seated in the connector molding. These contacts require shrink tubing after installation. These contact cannot be removed from connector after installation. Not suitable for fully loaded connector.

Note: Connectors can be kitted with all applicable crimp contacts, contact Technical Sales for connector part number.


FEMALE CONTACT

"CLOSED ENTRY" DESIGN



FEMALE	WIRE SIZE
PART NUMBER	AWG [mm²]
FC6018D2	18 [1.0] max

MALE CONTACT



MALE	WIRE SIZE
PART NUMBER	AWG [mm²]
MC6018D	18 [1.0] max


PROFESSIONAL LEVEL REMOVABLE CRIMP SIGNAL CONTACT

FOR USE WITH CBC AND QB SERIES CONNECTORS

SIZE 20

FEMALE CONTACT

"RUGGED OPEN ENTRY" DESIGN



Note: Connectors can be kitted with	
all applicable removable contacts	s,
contact Technical Sales for	
connector part number.	

FEMALE	WIRE SIZE
PART NUMBER	AWG [mm²]
FC6520D	<u>20 / 22 / 24</u> [0.5/0.3/0.25]

Authentic Positronic

REMOVABLE CONTACTS




REMOVABLE THERMOCOUPLE CRIMP CONTACT

FOR USE WITH CBC SERIES CONNECTORS

SIZE 20


FEMALE CONTACT

"CLOSED ENTRY" DESIGN



Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

MALE CONTACT



TYPE	MATERIAL	FEMALE PART NUMBER	MALE PART NUMBER	COLOR CODE	WIRE SIZE AWG [mm²]	ØA	ØВ
	CHROMEL (+)	FC6020D2CH [™]	MC6020DCH†	WHITE	20 / 22 / 24 [0.5 / 0.3 / 0.25]	0.066 [1.68]	0.045 [1.14]
K	CHNOIVIEL (+)	FC6026D2CH	MC6026DCH	WILL	26 / 28 / 30 [0.12 / 0.08 / 0.05]	0.048 [1.23]	0.027 [0.69]
`	ALUMEL (-)	FC6020D2AL**	MC6020DAL†	GREEN	20 / 22 / 24 [0.5 / 0.3 / 0.25]	0.066 [1.68]	0.045 [1.14]
	ALUWIEL (-)	FC6026D2AL	MC6026DAL	UNEEN	26 / 28 / 30 [0.12 / 0.08 / 0.05]	0.048 [1.23]	0.027 [0.69]
	COPPER (+)	FC6020D2CU**	MC6020DCU†	- RED	20 / 22 / 24 [0.5 / 0.3 / 0.25]	0.066 [1.68]	0.045 [1.14]
_T	with gold flash	FC6026D2CU	MC6026DCU		26 / 28 / 30 [0.12 / 0.08 / 0.05]	0.048 [1.23]	0.027 [0.69]
' [CONSTANTAN (-)	FC6020D2C0**	MC6020DC0†	YELLOW	20 / 22 / 24 [0.5 / 0.3 / 0.25]	0.066 [1.68]	0.045 [1.14]
	CONSTANTAN (-)	FC6026D2C0	MC6026DC0	TELLOW	26 / 28 / 30 [0.12 / 0.08 / 0.05]	0.048 [1.23]	0.027 [0.69]
	CUDOMEL (.)	FC6020D2CH ⁺⁺	MC6020DCH [†]	\A/I IITE	20 / 22 / 24 [0.5 / 0.3 / 0.25]	0.066 [1.68]	0.045 [1.14]
E	CHROMEL (+)	FC6026D2CH	MC6026DCH	WHITE	26 / 28 / 30 [0.12 / 0.08 / 0.05]	0.048 [1.23]	0.027 [0.69]
	CONSTANTAN ()	FC6020D2C0**	MC6020DCO [†]	VELLOW	20 / 22 / 24 [0.5 / 0.3 / 0.25]	0.066 [1.68]	0.045 [1.14]
	CONSTANTAN (-)	FC6026D2C0	MC6026DC0	YELLOW	26 / 28 / 30 [0.12 / 0.08 / 0.05]	0.048 [1.23]	0.027 [0.69]

For more information on the availability of Type J thermocouple contacts, and information about thermocouple contacts with PCB solder termination, please contact **Technical Sales.**

Chromel[®] and Alumel[®] are registered trademarks of Hoskins Manufacturing Company.

†Dimensionally equivalent to M39029/64-369

††Dimensionally equivalent to M39029/63-368


REMOVABLE CRIMP POWER CONTACT



*1 FEMALE CONTACT

MALE CONTACT "CLOSED ENTRY" DESIGN, L.S.A.

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.



FEMALE PART NUMBER	WIRE SIZE AWG [mm²]	ØA	ØВ	[1.588 ± 0.025]	MALE PART NUMBER	WIRE SIZE AWG [mm²]	ØA	ØВ
FC112N4S	12 / [4.0]	N/A	0.098 [2.49]	←	MC112NS-133.0	12 / [4.0]	N/A	0.098 [2.49]
FC112N4	12 / [4.0]	N/A	0.098 [2.49]	"S" in part number	MC112N-133.0	12 / [4.0]	N/A	0.098 [2.49]
FC114N4	14-16 [2.5-1.5]	0.105 [2.67]	0.081 [2.06]	indicates high	MC114N-133.0	14-16 [2.5-1.5]	0.105 [2.67]	0.081 [2.06]
FC116N4	16-18 [1.5-1.0]	0.093 [2.36]	0.067 [1.70]	conductiv- ity copper alloy	MC116N-133.0	16-18 [1.5-1.0]	0.093 [2.36]	0.067 [1.70]
FC120N4	20-22-24 [0.5-0.3-0.25]	0.068 [1.73]	0.045 [1.14]	material.	MC120N-133.0	20-22-24 [0.5-0.3-0.25]	0.068 [1.73]	0.045 [1.14]

*1 NOTE: Female contacts feature Large Surface Area (L.S.A.) closed entry contact design which provides maximum mating surfaces between male and female contact and reduced contact resistance during operation.

REMOVABLE

REMOVABLE CRIMP POWER CONTACT


FOR USE WITH CBD, CBC, CBCD AND CBDD SERIES CONNECTORS

SIZE 8

For contact current rating, see page 4.

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.

0.640 |-- [16.26]--| MAX.



FEMALE PART NUMBER	WIRE SIZE AWG [mm²]	Ø A
FC4008DS	8 [10.0]	<u>0.181</u> [4.60]
FC4008D	8 [10.0]	<u>0.181</u> [4.60]
FC4010D	10 [5.3]	<u>0.122</u> [3.10]
FC4012D	12 [4.0]	<u>0.101</u> [2.57]
FC4016D	16 [1.5]	<u>0.067</u> [1.70]

"S" in part number indicates high conductivity copper alloy material.

MALE PART NUMBER	WIRE SIZE AWG [mm²]	ØΑ
MC4008DS	8 [10.0]	<u>0.181</u> [4.60]
MC4008D	8 [10.0]	<u>0.181</u> [4.60]
MC4010D	10 [5.3]	<u>0.122</u> [3.10]
MC4012D	12 [4.0]	<u>0.101</u> [2.57]
MC4016D	16 [1.5]	<u>0.067</u> [1.70]

^{**} NOTE: Female contacts feature Large Surface Area (L.S.A.) closed entry contact design which provides maximum mating surfaces between male and female contact and reduced contact resistance during operation.

REMOVABLE SOLDER CUP POWER CONTACT

FOR USE WITH CBD, CBC, CBCD AND CBDD SERIES CONNECTORS

SIZE 8

For contact current rating, see page 4.

0.640 - [16.26] - MAX.

*1 FEMALE CONTACT


"CLOSED ENTRY" DESIGN, L.S.A.

0.858 [21.80]

ØA ØB

ØD.142 [3.61]

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.



FEMALE PART NUMBER	WIRE SIZE AWG [mm²]	Ø A	ØВ
FS4008D	8 [10.0]	<u>0.219</u> [5.56]	<u>0.188</u> [4.78]
FS4012D	12 [4.0]	<u>0.143</u> [3.63]	<u>0.112</u> [2.84]
FS4016D	16 [1.5]	<u>0.100</u> [2.54]	<u>0.069</u> [1.75]

MALE PART NUMBER	WIRE SIZE AWG [mm²]	Ø A	ØВ
MS4008D	8 [10.0]	<u>0.219</u> [5.56]	<u>0.188</u> [4.78]
MS4012D	12 [4.0]	<u>0.143</u> [3.63]	<u>0.112</u> [2.84]
MS4016D	16 [1.5]	<u>0.100</u> [2.54]	<u>0.069</u> [1.75]

^{*1} NOTE: Female contacts feature Large Surface Area (L.S.A.) closed entry contact design which provides maximum mating surfaces between male and female contact and reduced contact resistance during operation.



REMOVABLE HIGH VOLTAGE POWER CONTACT

FOR USE WITH CBD, CBC, CBCD AND CBDD SERIES CONNECTORS

SIZE 8


Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.


20

AWG


max.


STRAIGHT SOLDER WIRE TERMINATION





RIGHT ANGLE (90°) SOLDER WIRE TERMINATION






STRAIGHT PRINTED BOARD MOUNT POWER CONTACT

FOR USE WITH CBD AND CBDD SERIES CONNECTORS

SIZE 8

Positronic recommends printed circuit board termination contacts be supplied installed in the connector. Contact technical sales for part number information.

For contact current rating, see page 4.



*1 FEMALE CONTACT	
"CLOSED ENTRY" DESIGN, L.S.A.	MALE CONTACT
0.626 [15.90]	0.634 [16.10]
ØA P	ØA
Ø0.142 [3.61]	

FEMALE PART NUMBER	Ø A	CONTACT CODE
FDS4314D	<u>0.078</u> [1.98]	35
FDS4312D	<u>0.094</u> [2.39]	36
FDS4310D	<u>0.125</u> [3.18]	37

MALE PART NUMBER	Ø A	CONTACT CODE
MDS4314D	<u>0.078</u> [1.98]	35
MDS4312D	<u>0.094</u> [2.39]	36
MDS4310D	<u>0.125</u> [3.18]	37

^{*&#}x27;NOTE: Female contacts feature Large Surface Area (L.S.A.) closed entry contact design which provides maximum mating surfaces between male and female contact and reduced contact resistance during operation.

For information regarding crimp tool and crimping tool techniques, see Application Tools section, page 82.

REMOVABLE CONTACTS


RIGHT ANGLE (90°) PRINTED BOARD MOUNT POWER CONTACT

FOR USE WITH CBD AND CBDD SERIES CONNECTORS

SIZE 8

Positronic recommends printed circuit board termination contacts be supplied installed in the connector. Contact technical sales for part number information.

For contact current rating, see page 4.



*1 FEMALE CONTACT "CLOSED ENTRY" DESIGN, L.S.A. A Ø0.142 [3.61]

FEMALE PART NUMBER	A REF.	ØВ	С	SHELL SIZE	CONTACT CODE
FRT4314D	<u>0.580</u> [14.73]	<u>0.078</u> [1.98]	<u>0.339</u> [8.61]	1, 2, 3 & 4	55
FRT4414D	<u>0.692</u> [17.58]	<u>0.078</u> [1.98]	<u>0.451</u> [11.46]	5	55
FRT4714D	<u>0.661</u> [16.79]	<u>0.078</u> [1.98]	<u>0.420</u> [10.67]	1, 2, 3 & 4	75
FRT4814D	<u>0.773</u> [19.63]	<u>0.078</u> [1.98]	<u>0.520</u> [13.21]	5	75
FRT4310D	1.051 [26.70]	<u>0.125</u> [3.18]	<u>0.810</u> [20.57]	1, 2, 3 & 4	57
FRT4410D	1.051 [26.70]	<u>0.125</u> [3.18]	<u>0.810</u> [20.57]	5	57

MALE PART NUMBER	A REF.	ØВ	С	SHELL SIZE	CONTACT
MRT4314D	<u>0.580</u> [14.73]	<u>0.078</u> [1.98]	<u>0.339</u> [8.61]	1, 2, 3 & 4	55
MRT4414D	<u>0.692</u> [17.58]	<u>0.078</u> [1.98]	<u>0.451</u> [11.46]	5	55
MRT4714D	<u>0.661</u> [16.79]	<u>0.078</u> [1.98]	<u>0.420</u> [10.67]	1, 2, 3 & 4	75
MRT4814D	<u>0.773</u> [19.63]	<u>0.078</u> [1.98]	<u>0.520</u> [13.21]	5	75
MRT4310D	1.051 [26.70]	<u>0.125</u> [3.18]	<u>0.810</u> [20.57]	1, 2, 3 & 4	57
MRT4410D	1.051 [26.70]	<u>0.125</u> [3.18]	<u>0.810</u> [20.57]	5	57

^{*1}NOTE: Female contacts feature Large Surface Area (L.S.A.) closed entry contact design which provides maximum mating surfaces between male and female contact and reduced contact resistance during operation.




REMOVABLE SHIELDED CONTACT

FOR USE WITH CBD, CBC, CBCD AND CBDD SERIES CONNECTORS

SIZE 8

Note: Connectors can be kitted with all applicable removable contacts, contact Technical Sales for connector part number.



Ø0.040 [1.02]-

∟Ø0.152 [3.86]

TYPE OF CONTACT	FEMALE PART NUMBER	MALE PART NUMBER	Α	ØВ	C MAX.	RG CABLE NUMBER
SOLDER/CRIMP	FC4101D	MC4101D	0.929 [23.60]	0.040 [1.02]	0.739 [18.77]	178 B/U 196 B/U
SOLDER/CRIMP	FC4102D	MC4102D	0.929 [23.60]	0.067 [1.70]	0.739 [18.77]	179 B/U 316 /U
SOLDER/CRIMP	FC4103D	MC4103D	1.037 [26.34]	0.108 [2.74]	0.847 [21.51]	180 B/U
SOLDER/CRIMP	FC4104D	MC4104D	1.037 [26.34]	0.120 [3.05]	0.847 [21.51]	58 B/U
SOLDER/SOLDER	FS4101D	MS4101D	0.929 [23.60]	0.040 [1.02]	0.739 [18.77]	178 B/U 196 B/U
SOLDER/SOLDER	FS4102D	MS4102D	0.929 [23.60]	0.067 [1.70]	0.739 [18.77]	179 B/U 316 /U
SOLDER/SOLDER	FS4103D	MS4103D	1.037 [26.34]	0.108 [2.74]	0.847 [21.51]	180 B/U
SOLDER/SOLDER	FS4104D	MS4104D	1.037 [26.34]	0.120 [3.05]	0.847 [21.51]	58 B/U
CRIMP/CRIMP	FCC4101D	MCC4101D	0.929 [23.60]	0.040 [1.02]	0.739 [18.77]	178 B/U 196 B/U
CRIMP/CRIMP	FCC4102D	MCC4102D	0.929 [23.60]	0.067 [1.70]	0.739 [18.77]	179 B/U 316 /U
CRIMP/CRIMP	FCC4103D	MCC4103D	1.037 [26.34]	0.108 [2.74]	0.847 [21.51]	180 B/U
CRIMP/CRIMP	FCC4104D	MCC4104D	1.037 [26.34]	0.120 [3.05]	0.847 [21.51]	58 B/U



SHIELDED CONTACTS


Two-step crimping action for signal and shielding conductors.

STRAIGHT PRINTED BOARD MOUNTED SHIELDED CONTACT

FOR USE WITH CBD AND CBDD SERIES CONNECTORS

SIZE 8

Positronic recommends printed circuit board termination contacts be supplied installed in the connector. Contact technical sales for part number information.




RIGHT ANGLE (90°) PRINTED BOARD MOUNT SHIELDED CONTACT

FOR USE WITH CBD AND CBDD SERIES CONNECTORS

SIZE 8

Positronic recommends printed circuit board termination contacts be supplied installed in the connector. Contact technical sales for part number information.





SPECIAL OPTIONS APPENDIX

Combo-D D-Sub

MODIFICATION (MOS) SUFFIXES

Specify complete connector by selecting a base part number from the desired series Ordering Information Page. Once base part number is selected, add desired modifications (MOS) number below to the end of the part number.

Example part number: CBD17W2F55R7NT2X/AA-14-1062.1 (Ordering information pages can be found at the end of each series)

SERIES	CONNECTOR VARIANT	GENDER	TERMINATION TYPE AVAILABLE	MODIFICATIONS OF STANDARD OF STANDARD (MOS) SUFFIXES	DESCRIPTION OF MODIFICATION
CBD	3W3	F/M	0	-1841.0	Allows for molding to have positions A1 and A3 tooled only. Position A2 not molded but numbering will remain.
CBD	5W5	F/M	0	-1841.1	Allows for molding to have positions 1, 3 and 5 tooled only. Positions 2 and 4 not molded but numbering will remain.
CBD	8W8	F/M	0	-1841.2	Allows for molding to have positions A1,A3,A5 and A7 tooled only. Positions A2,A4,A6 and A8 not molded but numbering will remain.
CBD, CBM	3W3, 8W8	М	0	-1570.4	Integral stabilizing feature used to minimize size 8 contacts from floating in
CBC	36W4, 43W2	IVI	0	-1570.4	the molding. Use tool number 4311-0-1-0 to remove contact if necessary.
CBD, CBC, CBDD, CBHD, CBCD, CBDP*, ACBDP, ACBMP	ALL	F/M	ALL	-14	Allows connector with signal contacts installed, for signal contacts only to be plated 30µin [.76µm] gold over nickel.
CBD, CBC, CBDD, CBHD, CBCD, ACBDP, ACBMP	ALL	F/M	ALL	-14-1062.1	Allows connector with signal and power contacts installed, for both signal and power contacts to be plated 30µin [.76µm] gold over nickel.
CBD, CBC, CBDD, CBHD, CBCD, CBDP*, ACBDP, ACBMP	ALL	F/M	ALL	-15	Allows connector with signal contacts installed, for signal contacts only to be plated 50μin [1.27μm] gold over nickel.
CBD, CBC, CBDD, CBHD, CBCD, ACBDP, ACBMP	ALL	F/M	ALL	-15-1062.0	Allows connector with signal and power contacts installed, for both signal and power contacts to be plated 50μin [1.27μm] gold over nickel.
CBD, CBM, CBC, CBDD, CBHD, CBCD	ALL	F/M	ALL	-1062.0	Allows connector with power contacts installed, for the power contacts only to be plated 50µin [1.27µm] gold over nickel.
CBD, CBM, CBC, CBDD, CBHD, CBCD	ALL	F/M	ALL	-1062.1	Allows connector with power contacts installed, for the power contacts only to be plated 30μin [.76μm] gold over nickel.
CBD, CBM, CBC, CBDD, CBHD, CBCD	ALL	F/M	ALL	-759.0	Allows connectors to be supplied with blind mate guides, lockwashers and hexnuts installed. For connectors with a 4-40 threaded mounting style install blind mate guides only. For connectors with a R3/R6 mounting style install special blind mate guides with lockwashers and hexnuts. See D-subminiature Accessories catalog for more details.
CBD, CBM, CBC, CBDD, CBHD, CBCD	ALL	F/M	ALL	-759.1	Allows connector, with any contacts to include blind mate mounting plate. See D-subminiature Accessories catalog for more details.
QB	FOR CONTACTS	F	FC40**D CONTACTS	-1817.0	Allows for contacts to have a crimp barrel with a length of 0.310 [7.87].
QB	7W2, 9W4	М	56, 57	-1865.0	Connector with standard right angle (90°) brackets replaced with 4535-78-0 right angle (90°) brackets.
QB	7W2	М	N/A	-1845.0	Allows for a connector to be supplied with inverted bend. Contact tail length below bracket of 0.122 [3.10] max. Alignment bar not required.

MANY OTHER SPECIAL OPTIONS ARE AVAILABLE REFER TO D-SUBMINIATURE ACCESSORIES CATALOG, CONSULT TECHNICAL SALES OR VISIT OUR WEBSITE AT WWW.CONNECTPOSITRONIC.COM

CATIO N SE

CBD / CBM / CBC / CBCD connectors are offered

with *removable crimp contacts*. Positronic recognizes

the importance of supplying application tooling

to support our customers' use of our products.

Information on application tooling is

available on our web site at

www.connectpositronic.com/tooling

There you will find downloadable PDF cross reference charts for removable and compliant press-fit contacts. These charts will **supply part numbers** for insertion, removal and crimping tools, along with information regarding use of tools and techniques.



CONTACT APPLICATION TOOLS CROSS REFERENCE LIST

										U	SE	IND	ICA ⁻	TED	PC	SITI	RON	IIC .	TOC	DLS	FOF	R BI	EST	RE	SUL	.TS								
o	0 0	œ	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	Contact Size
* for complete listing of contact part numbers, see removable contact section pages 68-80.	MC4*20D	MS410*D	M\$401*D	MS4008D	MDS4*1*D	MDS4201D	MCC4104D	MCC4103D	MCC4102D	MCC4101D	MC410*D	MC401*D	MC4008DS	MC4008D	MA4063S	FS4*20D	FS410*D	FS401*D	FS4008D	FRT4*1*D	FRT4201D	FDS4*0*D	FCC4104D	FCC4103D	FCC4102D	FCC4101D	FC410*D	FC4012D-1817.0	FC401*D	FC4008DS	FC4008D-1817.0	FC4008D	FA4063S	Positronic Contact P/N
of contact part r							9504-15-0-0	9504-15-0-0	9504-13-0-0	9504-14-0-0	9504-0-0-0	9509-0-0-0	9504-19-0-0	9504-19-0-0									9504-15-0-0	9504-15-0-0	9504-13-0-0	9504-14-0-0	9504-0-0-0	9509-0-0-0	9509-0-0-0	9504-19-0-0	9504-19-0-0	9504-19-0-0		Handle & Positioner P/N
umbers, see re							9504-1-0-0	9504-1-0-0	9504-1-0-0	9504-1-0-0	9504-1-0-0	9509-1-0-0	9504-1-0-0	9504-1-0-0									9504-1-0-0	9504-1-0-0	9504-1-0-0	9504-1-0-0	9504-1-0-0	9509-1-0-0	0-0-1-6056	9504-1-0-0	9504-1-0-0	9504-1-0-0		Hand Crimp Tool P/N
movable co							HX4	HX4	HX4	HX4	HX4	M310	HX4	HX4									HX4	HX4	HX4	HX4	HX4	M310	M310	HX4	HX4	HX4		Mfg. Cross
ntact section par							M22520/5-01	M22520/5-01	M22520/5-01	M22520/5-01	M22520/5-01		M22520/5-01	M22520/5-01									M22520/5-01	M22520/5-01	M22520/5-01	M22520/5-01	M22520/5-01			M22520/5-01	M22520/5-01	M22520/5-01		Mii Equiv
ges 68-80.							9504-15-1-0	9504-15-1-0	9504-13-1-0	9504-14-1-0	9504-2-0-0	9509-2-0-0	9504-19-1-0	9504-19-1-0									9504-15-1-0	9504-15-1-0	9504-13-1-0	9504-14-1-0	9504-2-0-0	9509-2-0-0	9509-2-0-0	9504-19-1-0	9504-19-1-0	9504-19-1-0		Positioner
							Y877	Y877	Y937	Y878	Y322	TP-974	Y524	Y524									Y877	Y877	Y937	Y878	Y322	TP-974	TP-974	Y524	Y524	Y524		Mfg. Cross
																																		Mil Equiv
							N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A									N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A		Insertion Tool
																																		Mfg. Cross
																																		Mil Equiv
40-0-0-	1000	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	4311-0-0-0	Removal Tool
7	0 -	P+	P+	P+	P+	P+	P+	P ₊	P+	P+	P+	P ₊	P +	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	P+	Mfg. Cross
																																		Mii Equiv

APPLICATION TOOLS



CONTACT APPLICATION TOOLS CROSS REFERENCE LIST

USE INDICATED POSITRONIC TOOLS FOR BEST RESULTS.

							- 00	JL 11 V			1 00		JINIC	100	LOI)LO1	RES	OLI) 						
16	16	16	16	16	16	20	20	20	20	20	20	20	20	20	20	20	20	22	23	22	22	22	22	22	22	Contact Size
MC120N-133.0	MC112NS-133.0	MC11*N-133.0	FC120N4	FC112N4S	FC11*N4	MC6026D** Thermocouple	MC6026D	MC6020D** Thermocouple	MC6020D	MC6018D	M39029/6*-36*	FC6520D	FC6026D2** Thermocouple	FC6026D2	FC6020D2** Thermocouple	FC6020D2	FC6018D2	M39029/58-360	M39029/57-354	MC8022D** Thermocouple	MC8022D	MC8020D	FC8022D2** Thermocouple	FC8022D2	FC8020D2	Positronic Contact P/N
																										Handle & Positioner P/N
9501-0-0-0	9509-4-0-0	9501-0-0-0	9501-0-0-0	9509-4-0-0	9501-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	9507-0-0-0	Hand Crimp Tool P/N
AF8	GS222	AF8	AF8	GS222	AF8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	AFM8	Mfg. Cross
M22520/1-01		M22520/1-01	M22520/1-01		M22520/1-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	M22520/2-01	Mil Equiv
9502-17-0-0	9509-5-0-0	9502-17-0-0	T.B.D.	9509-5-0-0	T.B.D.	9502-5-0-0	9502-5-0-0	9502-5-0-0	9502-5-0-0	9502-11-0-0	9502-5-0-0	9502-5-0-0	9502-5-0-0	9502-5-0-0	9502-5-0-0	9502-5-0-0	9502-11-0-0	9502-4-0-0	9502-3-0-0	9502-4-0-0	9502-4-0-0	9502-29-0-0	9502-3-0-0	9502-3-0-0	9502-29-0-0	Positioner
TP1110	TP1366	TP1110	T.B.D.	TP1366	T.B.D.	K13-1	K13-1	K13-1	K13-1	K774	K13-1	K13-1	K13-1	K13-1	K13-1	K13-1	K774	K42	K41	K-42	K-42	K1665	K-41	K-41	K1665	Mfg. Cross
						M22520/2-08	M22520/2-08	M22520/2-08	M22520/2-08		M22520/2-08	M22520/2-08	M22520/2-08	M22520/2-08	M22520/2-08	M22520/2-08		M22520/2-09	M22520/2-06	M22520/2-09	M22520/2-09		M22520/2-06	M22520/2-06		Mil Equiv
9099-0-0-0	9099-0-0-0	9099-0-0-0	9099-0-0-0	9099-0-0-0	9099-0-0-0	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04		Insertion Tool
ITH 1094	ITH 1094	ITH 1094	ITH 1094	ITH 1094	ITH 1094	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-1	91067-1	91067-1	91067-1	91067-1	91067-1	91067-1		Mfg. Cross
M81969/18-01	M81969/18-01	M81969/18-01	M81969/18-01	M81969/18-01	M81969/18-01	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04		Mil Equiv
9081-0-0-0	9081-0-0-0	9081-0-0-0	9081-0-0-0	9081-0-0-0	9081-0-0-0	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04		Removal Tool
RTG 2103	RTG 2103	RTG 2103	RTG 2103	RTG 2103	RTG 2103	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-2	91067-1	91067-1	91067-1	91067-1	91067-1	91067-1	91067-1		Mfg. Cross
RTG 2103 M81969/20-01	M81969/20-01	RTG 2103 M81969/20-01	M81969/20-01	M81969/20-01	M81969/20-01	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-02	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04	M81969/1-04		Mii Equiv

* for complete listing of contact part numbers, see removable contact section pages 68-80.



SUGGESTED PRINTED BOARD HOLE SIZES FOR COMPLIANT PRESS-FIT CONNECTORS

Traditionally, tin-lead has been a popular plating for printed circuit board (PCB) holes. However, many PCB hole platings must now be RoHS Compliant. Positronic is pleased to offer **PCB HOLE SIZE FOR RoHS** PCB plating as shown below.

OMEG	iA & BI-SPR	ING COMPLIAN	T PRESS-FIT CON	ITACT HOLE
BOARD TYPE	CONTACT SIZE / TYPE	RECOMMENDED DRILL HOLE SIZE	RECOMMENDED PLATING	FINISHED HOLE SIZES
	22 OMEGA	<u>Ø0.0453±0.0010</u> [Ø1.150±0.025]		<u>Ø0.0394+0.0035-0.0024</u> [Ø1.000+0.090-0.060]
TIN-LEAD SOLDER	20 OMEGA	<u>Ø0.0453±0.0010</u> [Ø1.150±0.025]	0.0006 [15µ] minimum solder	<u>Ø0.0394+0.0035-0.0024</u> [Ø1.000+0.090-0.060]
PCB	16 BI-SPRING	<u>Ø0.069±0.001</u> [Ø1.750±0.025]	over 0.0010 [25µ] min. copper	<u>Ø0.0630+0.0035-0.0024</u> [Ø1.600+0.090-0.060]
	8 BI-SPRING	<u>Ø0.125±0.001</u> [Ø3.180±0.025]		<u>ø0.119±0.002</u> [ø3.02±0.05]
		RoHS PCB PLATI	NG OPTIONS	
	22 OMEGA	<u>ø0.047±0.001</u> [ø1.19±0.025]		<u>ø0.043±0.002</u> [ø1.09±0.05]
COPPER PCB	20 OMEGA	<u>Ø0.047±0.001</u> [Ø1.19±0.025]	0.0010 [25µ]	<u>Ø0.043±0.002</u> [Ø1.09±0.05]
	16 BI-SPRING	<u>Ø0.069±0.001</u> [Ø1.750±0.025]	min. copper	<u>Ø0.0630+0.0035-0.0024</u> [Ø1.600+0.090-0.060]
	8 BI-SPRING	<u>Ø0.125±0.001</u> [Ø3.180±0.025]		<u>Ø0.119±0.002</u> [Ø3.02±0.05]
	22 OMEGA	<u>Ø0.047±0.001</u> [Ø1.19±0.025]		<u>Ø0.043±0.002</u> [Ø1.09±0.05]
IMMERSION TIN	20 OMEGA	<u>Ø0.047±0.001</u> [Ø1.19±0.025]	0.000033±0.000006 [0.85±0.15µ] immersion tin	<u>Ø0.043±0.002</u> [Ø1.09±0.05]
PCB	16 BI-SPRING	<u>Ø0.069±0.001</u> [Ø1.750±0.025]	over 0.0010 [25µ] min. copper	<u>Ø0.0630+0.0035-0.0024</u> [Ø1.600+0.090-0.060]
	8 BI-SPRING	<u>ø0.125±0.001</u> [ø3.180±0.025]		<u>ø0.119±0.002</u> [ø3.02±0.05]
	22 OMEGA	<u>ø0.047±0.001</u> [ø1.19±0.025]		<u>Ø0.043±0.002</u> [Ø1.09±0.05]
IMMERSION SILVER	20 OMEGA	<u>ø0.047±0.001</u> [ø1.19±0.025]	0.000013±0.000007 [0.34±0.17µ] immersion silver	<u>Ø0.043±0.002</u> [Ø1.09±0.05]
PCB	16 BI-SPRING	<u>Ø0.069±0.001</u> [Ø1.750±0.025]	over 0.0010 [25µ] min. copper	<u>Ø0.0630+0.0035-0.0024</u> [Ø1.600+0.090-0.060]
	8 BI-SPRING	<u>Ø0.125±0.001</u> [Ø3.180±0.025]		<u>ø0.119±0.002</u> [ø3.02±0.05]
	22 OMEGA	<u>ø0.047±0.001</u> [ø1.19±0.025]	0.000002 [0.05µ] min.	<u>ø0.043±0.002</u> [ø1.09±0.05]
ELECTROLESS NICKEL / IMMERSION GOLD PCB	20 OMEGA	<u>ø0.047±0.001</u> [ø1.19±0.025]	immersion gold over 0.000177±0.000059 [4.5±1.5µ] electroless	<u>ø0.043±0.002</u> [ø1.09±0.05]
	16 BI-SPRING	<u>Ø0.069±0.001</u> [Ø1.750±0.025]	nickel per IPC-4552 over 0.0010 [25µ]	<u>Ø0.0630+0.0035-0.0024</u> [ø1.600+0.090-0.060]
	8 BI-SPRING	<u>Ø0.125±0.001</u> [Ø3.180±0.025]	min. copper	<u>Ø0.119±0.002</u> [Ø3.02±0.05]

"Omega" Termination


utilized on signal contacts



"Bi-Spring" Termination

utilized on signal contacts





COMPLIANT PRESS-FIT TERMINATION CONTACT HOLE

NOTE: For PCB plating compositions not shown, consult Technical Sales.

COMPLIANT PRESS-FIT USER INFORMATION


When properly used, Positronic Industries Bi-Spring Power or Omega Signal Press-Fit terminations provide reliable service even under severe conditions.

Connectors utilizing this leading technology press-fit contact are easy to install:

- Inexpensive installation tooling is available from Positronic, to choose the proper installation tool refer to page 86 for part number ordering information.
- 2. Insert the connector into the P.C. board or backplane and seat connector fully.
- 3. Secure the connector to the P.C. board or backplane using two self-tapping screws. The screws should be 4-40 threads supplied by customer.

USE INDICATED POSITRONIC TOOLS FOR BEST RESULTS

SEATING TOOLS



Positronic offers expert assistance in adapting application tooling to your manufacturing environment. Contact our application tooling specialist for assistance.

POSITRONIC RECOMMENDED TOOLS FOR COMPLIANT PRESS-FIT CONNECTORS AND CONTACTS

SHELL	CONNECTOR VARIANT		IG TOOL WITH ARBOR SHAFT	ARBOR PRESS FOR SEATING TOOLS	REPLACEMENT PINS FOR CONNECTOR		
		FEMALE P / N	MALE P / N		SEATING TOOL		
	2WK2	9512-44-0-41	9512-44-0-41				
1	5W1	9512-18-0-41	9512-1-0-41				
	8W2	9512-41-0-41	9512-40-0-41		For 8W2 Size 22 Female contacts		
	3W3	9512-19-0-41	9512-2-0-41		use pin p / n 9512-41-3-41		
	зwкз	9512-39-0-41	9512-38-0-41		9512-41-3-41		
2	7W2	9512-20-0-41	9512-2-0-41		For 19W1 Size 22		
	11W1	9512-21-0-41	9512-2-0-41		Female contacts		
	19W1		use pin p / n 855-347-29-41				
	5W5	5W5 9512-22-0-41 9512-3-0-41					
	9W4	9512-23-0-41 9512-3-0-41			For Size 20		
3	13 W 3	9512-24-0-41	9512-3-0-41		Female contacts use pin p / n		
	17W2	9512-25-0-41	9512-3-0-41	Use 1 ton capacity	855-347-18-41		
	21W1	9512-26-0-41	9512-3-0-41	4 inch throat	F 0! 40		
	8W8	9512-27-0-41	9512-4-0-41		For <u>Size 16</u> Female contacts		
	13W6	9512-28-0-41	9512-4-0-41		use pin p / n 855-347-28-41		
4	17W5	9512-29-0-41	9512-4-0-41		333 311 23 11		
4	21WA4	9512-30-0-41	9512-4-0-41] Fc	For <u>Size 8</u>		
	25W3	9512-31-0-41	9512-4-0-41		Female contacts use pin p / n		
	27W2	9512-32-0-41	9512-4-0-41		855-347-19-41		
	24W7	9512-33-0-41	9512-5-0-41				
5	36W4	9512-34-0-41	9512-5-0-41		Male contacts		
5	43W2	9512-35-0-41	9512-5-0-41		don't use replaceable pins		
	47W1 9512-36-0-41 9512-5-0-41						
6	46W4	9512-37-0-41	9512-16-0-41				



Positronic® offers a variety of QPL connector products

D-SUBMINIATURE CONNECTORS

MIL PREFIX	POSITRONIC SERIES
MIL-DTL-24308/1	HDC
MIL-DTL-24308/2	RD, DD
MIL-DTL-24308/3	HDC
MIL-DTL-24308/4	RD, DD
MIL-DTL-24308/5	HDC
MIL-DTL-24308/6	RD, DD
MIL-DTL-24308/7	HDC
MIL-DTL-24308/8	RD, DD
MIL-DTL-24308/23	HDC, DD

MIL PREFIX	POSITRONIC SERIES
MIL-DTL-24308/24	HDC, DD
MIL-DTL-24308/25	HDC, RD, DD
MIL-DTL-24308/26	HDC, RD, DD
GSFC S-311-P4	SND, SDD, SCBC, SCBM
GSFC S-311-P10	SND, SCBM
SAE AS39029/57	DD
SAE AS39029/58	DD
SAE AS39029/63	RD
SAE AS39029/64	RD

RECTANGULAR CONNECTORS

MIL PREFIX	POSITRONIC SERIES
MIL-DTL-28748/3	GMCT
MIL-DTL-28748/4	GMCT
MIL-DTL-28748/5	GM
MIL-DTL-28748/6	GM
MIL-DTL-28748/7	SGM

MIL PREFIX	POSITRONIC SERIES
MIL-DTL-28748/8	SGM
MIL-C-28748/13	SGMC
MIL-C-28748/14	SGMC
SAE AS39029/34	SGMC, GMCT
SAE AS39029/35	SGMC, GMCT

For a complete QPL listing available to download in PDF format, visit the desired connector family home page and click on link "Qualified Product Listing (PDF)" on our website at:

www.connectpositronic.com

or enter the URL link below to download the QPL PDF file immediately!

www.connectpositronic.com/qpl/catalog

rcellence Positronic HIGH RELIABILITY Products ome

O W



FEATURES:

- High current density Energy saving low contact resistance • Hot swap capability
- AC/DC operation in a single connector Signal contacts for hardware manage-
- ment Blind mating Sequential mating Large surface area contact mating system
- Wide variety of accessories
- Customer-specified contact arrangements
- Modular tooling which produces a single piece connector insert

Contact Sizes: **Current Ratings:** Terminations:

0, 8, 12, 16, 20, 22 and 24 To 200 amperes per contact

Crimp and fixed cable connector, straight solder, right angle (90°) solder, straight compliant press-in and right angle (90°) compliant

Multiple variants in a variety of package sizes PICMG 2.11, PICMG 3.0, VITA 41, DSCC, GSFC S-311-P-4, Configurations: Compliance:

GSFC S-311-P-10

BMINIA FEATURES:



Contact Sizes: **Current Ratings:** Terminations:

8, 16, 20 and 22 To 100 amperes

Configurations:

Qualifications:

thermocouple and air coupling contacts; environmentally sealed and dual port connector packages including mixed density Broad selection of accessories

 Size 20 and 22 contacts suitable for use in carrying power

Options include high voltage, coax,

Four performance levels available for

best cost/performance ratio: professional, industrial, military and space-flight quality

IP65, IP67

Crimp, wire solder, straight solder, right angle (90°) solder, straight compliant press-in and right angle (90°) compliant press-in Multiple variants in both standard and high densities, seven connector

MIL-DTL-24308, GSFC S-311-P-4, GSFC S-311-P-10,

FEATURES:

- Two performance levels available: industrial quality and military quality
- A wide variety of accessories
- Broad selection of contact arrangement
- Connector coding device (keying) options

Contact Sizes: Current Ratings: Terminations:

Configurations:

16, 20 and 22

To 13 amperes nominal

Crimp, wire solder, straight solder, right angle (90°) solder, and straight compliant press-in

Multiple variants in both standard and high densities,

Qualifications: MIL-DTL-28748, AS39029, CCITT V.35

C U L A



FEATURES:

- Non-corrodible / lightweight composite construction
- EMI/RFI shielded versions
- Thermocouple contacts
- Environmentally sealed versions
- Rear insertion/ front release of removable contacts
- Two level sequential mating
- Overmolding available on full assemblies

FEATURES: • Intended for use as an electrical

feedthrough in high vacuum applications

• Helium leakage rate at ambient temperature: < 5x10-9 mbar.l/s under

Signal, power, coax and high voltage

Connectors can be mounted on flange

assembly per customer specification

a vacuum 1.5x10⁻² mbar

versions available

Contact Sizes:

12, 16, 20 and 22

Crimp, wire solder, straight solder, and right angle (90°) solder Multiple variants in four package sizes Environmental protection to IP67

Current Ratings:

Terminations: Configurations: Qualifications:



FEATURES:

- Shorten the supply chain and reduce additional costs and delays by "cablizing" your Positronic connector selection
- Overmolding available
- Shielded and environmentally sealed versions available
- Power cables and access boxes which meet the SAE J2496 specification
- Design assemblies in accordance with customer specifications.
- Prepare wire harness connector configuration and performance specifications.
- Design each system in accordance with applicable customer, domestic, and international standards.
- Define and conduct performance and verification testing.



Current Ratings: Terminations:

Configurations:

Compliance:

8, 12, 16, 20 and 22

To 40 amperes nominal

Feedthrough is standard; flying leads and board mount available See D-subminiature and circular configurations above Space-D32

For more information, visit www.connectpositronic.com or call your nearest Positronic sales office listed on the back of this catalog.



an Amphenol company

Divisional Headquarters

Positronic | Americas

1325 N Eldon Ave Springfield MO 65803 USA +1 800 641 4054 info@connectpositronic.com

Positronic | Europe

Z.I. d'Engachies46, route d'EngachiesF-32020 Auch Cedex 9 France

+33 5 6263 4491 contact@connectpositronic.com

Positronic | Asia

3014A Ubi Rd 1 #07-01 Singapore 408703 +65 6842 1419

singapore@connectpositronic.com

Sales Offices

Positronic has local sales representation all over the world. To find the nearest sales office, please visit www.connectpositronic.com/sales