

Dual, 14-Bit, 80 MSPS/125 MSPS, Serial LVDS 1.8 V Analog-to-Digital Converter

FEATURES

- ▶ 1.8 V supply operation
- ▶ Low power: 122 mW per channel at 125 MSPS with scalable power options
- ▶ SNR = 74 dBFS (to Nyquist); SFDR = 91 dBc at 70 MHz
- \triangleright DNL = ±0.65 LSB (typical); INL = ±1.5 LSB (typical)
- Serial LVDS (ANSI-644, default) and low power, reduced range option (similar to IEEE 1596.3)
- ▶ 650 MHz full power analog bandwidth
- ▶ 2 V p-p input voltage range
- Serial port control
 - ► Full chip and individual channel power-down modes
 - ► Flexible bit orientation
 - Built-in and custom digital test pattern generation
 - Clock divider
 - ▶ Programmable output clock and data alignment
 - ▶ Programmable output resolution
 - Standby mode
- ▶ AEC-Q100 qualified for automotive applications

APPLICATIONS

- Communications
- Diversity radio and smart antenna systems
- Multimode digital receivers
- ▶ GSM, EDGE, W-CDMA, LTE, CDMA2000, WiMAX, TD-SCDMA
- ▶ I/Q demodulation systems
- ▶ Broadband data applications
- Battery-powered instruments
- Handheld scope meters
- ▶ Portable medical imaging and ultrasound
- ▶ Radar/LIDAR

PRODUCT HIGHLIGHTS

- Small Footprint. Two ADCs are contained in a small, space-saving package.
- 2. Low Power. The AD9645 uses 122 mW/channel at 125 MSPS with scalable power options.
- **3.** Pin Compatibility with the AD9635, a 12-Bit Dual ADC.
- Ease of Use. A data clock output (DCO) operates at frequencies of up to 500 MHz and supports double data rate (DDR) operation.
- **5.** User Flexibility. SPI control offers a wide range of flexible features to meet specific system requirements.

FUNCTIONAL BLOCK DIAGRAM




Figure 1.

GENERAL DESCRIPTION

The AD9645 is a dual, 14-bit, 80 MSPS/125 MSPS analog-to-digital converter (ADC) with an on-chip sample-and-hold circuit designed for low cost, low power, small size, and ease of use. The product operates at a conversion rate of up to 125 MSPS and is optimized for outstanding dynamic performance and low power in applications where a small package size is critical.

The ADC requires a single 1.8 V power supply and LVPECL-/ CMOS-/LVDS-compatible sample rate clock for full performance operation. No external reference or driver components are required for many applications.

The ADC automatically multiplies the sample rate clock for the appropriate LVDS serial data rate. A data clock output (DCO) for capturing data on the output and a frame clock output (FCO) for signaling a new output byte are provided. Individual channel power-down is supported; the AD9645 typically consumes less than 2 mW in the full power-down state. The ADC provides several features designed to maximize flexibility and minimize system cost, such as programmable output clock and data alignment and digital test pattern generation. The available digital test patterns include built-in deterministic and pseudo-random patterns, along with custom user-defined test patterns entered via the serial port interface (SPI).

The AD9645 is available in a RoHS-compliant, 32-lead LFCSP. It is specified over the automotive temperature range of -40°C to +105°C.

TABLE OF CONTENTS

Features	1	Configuration Using the SPI	28
Applications	1	Hardware Interface	29
Product Highlights	1	Configuration Without the SPI	29
Functional Block Diagram	1	SPI Accessible Features	29
General Description	1	Memory Map	30
Specifications	4	Reading the Memory Map Register Table	
DC Specifications	4	Open Locations	
AC Specifications		Default Values	30
Digital Specifications	6	Logic Levels	30
Switching Specifications		Channel-Specific Registers	30
Timing Specifications		Memory Map Register Table	
Timing Diagrams		Memory Map Register Descriptions	
Absolute Maximum Ratings		Device Index (Register 0x05)	
Thermal Resistance		Transfer (Register 0xFF)	
ESD Caution	11	Power Modes (Register 0x08)	
Pin Configuration and Function Descriptions		Enhancement Control (Register 0x0C)	
Typical Performance Characteristics		Output Mode (Register 0x14)	
AD9645-80		Output Adjust (Register 0x15)	
AD9645-125	17	Output Phase (Register 0x16)	
Equivalent Circuits		Serial Output Data Control (Register 0x21)	
Theory of Operation		Resolution/Sample Rate Override (Register	
Analog Input Considerations		0x100)	35
Input Common Mode		User I/O Control 2 (Register 0x101)	
Differential Input Configurations		User I/O Control 3 (Register 0x102)	
Voltage Reference		Applications Information	
Clock Input Considerations		Design Guidelines	
Clock Input Options		Power and Ground Guidelines	
Input Clock Divider		Clock Stability Considerations	
Clock Duty Cycle		Exposed Pad Thermal Heat Slug	
Jitter Considerations		Recommendations	37
Power Dissipation and Power-Down Mode		VCM	
Digital Outputs and Timing		Reference Decoupling	
SDIO/PDWN Pin		SPI Port	
SCLK/DFS Pin		Outline Dimensions	
CSB Pin		Ordering Guide	
RBIAS Pin		Evaluation Boards	
Output Test Modes		Automotive Products	
Serial Port Interface (SPI)			
DEV//01011 11070 DV/			
REVISION HISTORY			
5/2023—Rev. B to Rev. C			
			1
<u> </u>			
·			
•		Output Offset Voltage (VOS) W Grade Parameter	3
		ced Signal Option, Output Offset Voltage (VOS)	
			6
TO CIAGO I GIGINOLOI, IGDIC U			0

Rev. C | 2 of 38

TABLE OF CONTENTS

Changes to Table 6	11
Added Figure 12 and Figure 13; Renumbered Sequentially	13
Changes to Figure 21	
Moved Figure 55 and Figure 56	
Changes to Figure 58	
Changes to Digital Outputs and Timing Section	
Changes to Table 10	
Changes to Table 11	27
Changes to Output Test Modes Section	
Changes to Table 16	
Updated Outline Dimensions	
Changes to Ordering Guide	
Added Automotive Products Section	

SPECIFICATIONS

DC SPECIFICATIONS

AVDD = 1.8 V, DRVDD = 1.8 V, 2 V p-p differential input, 1.0 V internal reference, AIN = -1.0 dBFS, unless otherwise noted.

Table 1.

			AD9645-	80		AD9645V	<i>l</i> -80		AD9645-	125	
Parameter ¹	Temp	Min	Тур	Max	Min	Тур	Max	Min	Тур	Max	Unit
RESOLUTION		14			14			14			Bits
ACCURACY											
No Missing Codes	Full		Guarante	ed		Guarante	eed		Guarante	ed	
Offset Error	Full	-0.6	-0.2	+0.1	-0.7	-0.2	+0.35	-0.6	-0.2	+0.2	% FS
Offset Matching	Full	-0.2	+0.1	+0.4	-0.33	+0.1	+0.6	-0.2	+0.1	+0.4	% FS
Gain Error	Full	-4.3	-1.0	+2.2	-5.0	-1.5	+2.2	-5.1	-1.5	+2.3	% FS
Gain Matching	Full		0.5	2.2		0.5	2.62		0.6	2.6	% FS
Differential Nonlinearity (DNL)	Full	-0.6		+1.3	-0.65		+1.4	-0.6		+1.3	LSB
	25°C		±0.65			±0.65			±0.65		LSB
Integral Nonlinearity (INL)	Full	-2.6		+2.8	-2.8		+2.8	-3.6		+3.4	LSB
, ,	25°C		±1.1			±1.1			±1.5		LSB
TEMPERATURE DRIFT											
Offset Error	Full		2.7			2.7			3.3		ppm/
NTERNAL VOLTAGE REFERENCE											1
Output Voltage (1 V Mode)	Full	0.98	1.0	1.02	0.98	1.0	1.02	0.98	1.0	1.02	V
Load Regulation at 1.0 mA (V _{REF} = 1 V)	25°C		2			2			2		mV
Input Resistance	25°C		- 7.5			7.5			7.5		kΩ
INPUT-REFERRED NOISE											1
V _{REF} = 1.0 V	25°C		0.95			0.95			1.0		LSBr
ANALOG INPUTS											
Differential Input Voltage (V _{REF} = 1 V)	Full		2			2			2		V p-p
Common-Mode Voltage	Full		0.9			0.9			0.9		V
Common-Mode Range	25°C	0.5		1.3	0.5		1.3	0.5		1.3	V
Differential Input Resistance	25°C		5.2			5.2			5.2		kΩ
Differential Input Capacitance	25°C		3.5			3.5			3.5		pF
POWER SUPPLY											'
AVDD	Full	1.7	1.8	1.9	1.7	1.8	1.9	1.7	1.8	1.9	V
DRVDD	Full	1.7	1.8	1.9	1.7	1.8	1.9	1.7	1.8	1.9	V
I _{AVDD} ²	Full		56	61		56	61		78	83	mA
I _{DRVDD} (ANSI-644 Mode) ²	Full		48	50		48	52		57	60	mA
I _{DRVDD} (Reduced Range Mode) ²	25°C		39	00		39	02		48	00	mA
TOTAL POWER CONSUMPTION	200								10		11111
DC Input	Full		178	191		178	191		227	244	mW
Sine Wave Input (Two Channels; Includes Output Driv-	Full		187	200		187	200		243	257	mW
ers in ANSI-644 Mode)				200			200			201	11100
Sine Wave Input (Two Channels; Includes Output Drivers in Reduced Range Mode)	25°C		171			171			227		mW
Power-Down	25°C		2			2			2		mW
Standby ³	Full		92	101		92	101		115	126	mW

¹ See the AN-835 Application Note, *Understanding High Speed ADC Testing and Evaluation*, for definitions and for details on how these tests were completed.

analog.com Rev. C | 4 of 38

² Measured with a low input frequency, full-scale sine wave on both channels.

³ Can be controlled via the SPI.

SPECIFICATIONS

AC SPECIFICATIONS

AVDD = 1.8 V, DRVDD = 1.8 V, 2 V p-p differential input, 1.0 V internal reference, AIN = -1.0 dBFS, unless otherwise noted.

Table 2.

			AD9645	80		AD9645V	V-80		AD9645-	125	_
Parameter ¹	Temp	Min	Тур	Max	Min	Тур	Max	Min	Тур	Max	Unit
SIGNAL-TO-NOISE RATIO (SNR)											
f _{IN} = 9.7 MHz	25°C		75.6			75.6			75.2		dBFS
f _{IN} = 30.5 MHz	25°C		75.4			75.4			75.0		dBFS
f _{IN} = 70 MHz	Full	73.1	74.5		72.4	74.5		72.8	74.3		dBFS
f _{IN} = 139.5 MHz	25°C		72.1			72.1			72.5		dBFS
f _{IN} = 200.5 MHz	25°C		70.0			70.0			70.3		dBFS
SIGNAL-TO-NOISE-AND-DISTORTION RATIO (SINAD)											
f _{IN} = 9.7 MHz	25°C		75.6			75.6			75.1		dBFS
f _{IN} = 30.5 MHz	25°C		75.2			75.2			75.0		dBFS
f _{IN} = 70 MHz	Full	72.7	74.4		72.0	74.4		72.4	74.2		dBFS
f _{IN} = 139.5 MHz	25°C		71.7			71.7			72.4		dBFS
f _{IN} = 200.5 MHz	25°C		69.7			69.7			70.0		dBFS
EFFECTIVE NUMBER OF BITS (ENOB)											
f _{IN} = 9.7 MHz	25°C		12.3			12.3			12.2		Bits
f _{IN} = 30.5 MHz	25°C		12.2			12.2			12.2		Bits
f _{IN} = 70 MHz	Full	11.8	12.1		11.8	12.1		11.7	12.0		Bits
f _{IN} = 139.5 MHz	25°C		11.6			11.6			11.7		Bits
f _{IN} = 200.5 MHz	25°C		11.3			11.3			11.3		Bits
SPURIOUS-FREE DYNAMIC RANGE (SFDR)											
f _{IN} = 9.7 MHz	25°C		96			96			93		dBc
f _{IN} = 30.5 MHz	25°C		91			91			97		dBc
f _{IN} = 70 MHz	Full	82	96		82	93		82	91		dBc
f _{IN} = 139.5 MHz	25°C		82			82			91		dBc
f _{IN} = 200.5 MHz	25°C		82			82			81		dBc
WORST HARMONIC (SECOND OR THIRD)											
f _{IN} = 9.7 MHz	25°C		-96			-96			-93		dBc
f _{IN} = 30.5 MHz	25°C		-91			-91			-97		dBc
f _{IN} = 70 MHz	Full		-96	-83		-96	-83		-91	-82	dBc
f _{IN} = 139.5 MHz	25°C		-82			-82			-93		dBc
f _{IN} = 200.5 MHz	25°C		-82			-82			-81		dBc
WORST OTHER HARMONIC OR SPUR											
f _{IN} = 9.7 MHz	25°C		-99			-99			-96		dBc
f _{IN} = 30.5 MHz	25°C		-97			-97			-99		dBc
f _{IN} = 70 MHz	Full		-99	-82		-99	-82		-96	-84	dBc
f _{IN} = 139.5 MHz	25°C		-93			-93			-91		dBc
f _{IN} = 200.5 MHz	25°C		-91			- 91			-87		dBc
TWO-TONE INTERMODULATION DISTORTION (IMD)— AIN1 AND AIN2 = -7.0 dBFS											
$f_{\text{IN1}} = 70.5 \text{ MHz}, f_{\text{IN2}} = 72.5 \text{ MHz}$	25°C		-93			-93			-93		dBc
CROSSTALK ²	25°C		-97			-97			- 97		dB
CROSSTALK (OVERRANGE CONDITION) ³	25°C		-97			-97			-97		dB
POWER SUPPLY REJECTION RATIO (PSRR) ⁴	200								- 01		40
OWEN OUT ET NEUEUTION INTO (LONN)	25°C		42			42			42		dB

analog.com Rev. C | 5 of 38

SPECIFICATIONS

Table 2. (Continued)

			AD9645-80		AD9645W-80			AD9645-125			
Parameter ¹	Temp	Min	Тур	Max	Min	Тур	Max	Min	Тур	Max	Unit
DRVDD	25°C		67			67			67		dB
ANALOG INPUT BANDWIDTH, FULL POWER	25°C		650			650			650		MHz

¹ See the AN-835 Application Note, Understanding High Speed ADC Testing and Evaluation, for definitions and for details on how these tests were completed.

DIGITAL SPECIFICATIONS

AVDD = 1.8 V, DRVDD = 1.8 V, 2 V p-p differential input, 1.0 V internal reference, AIN = −1.0 dBFS, unless otherwise noted.

Table 3.

Parameter ¹	Temp	Min	Тур	Max	Unit
CLOCK INPUTS (CLK+, CLK-)					
Logic Compliance			CMOS/LVDS/L	VPECL	
Differential Input Voltage ²	Full	0.2		3.6	V p-p
Input Voltage Range	Full	AGND - 0.2		AVDD + 0.2	V
Input Common-Mode Voltage	Full		0.9		V
Input Resistance (Differential)	25°C		15		kΩ
Input Capacitance	25°C		4		pF
LOGIC INPUT (SCLK/DFS)					
Logic 1 Voltage	Full	1.2		AVDD + 0.2	V
Logic 0 Voltage	Full	0		0.8	V
Input Resistance	25°C		30		kΩ
Input Capacitance	25°C		2		pF
LOGIC INPUT (CSB)					
Logic 1 Voltage	Full	1.2		AVDD + 0.2	V
Logic 0 Voltage	Full	0		0.8	V
Input Resistance	25°C		26		kΩ
Input Capacitance	25°C		2		pF
LOGIC INPUT (SDIO/PDWN)					
Logic 1 Voltage	Full	1.2		AVDD + 0.2	V
Logic 0 Voltage	Full	0		0.8	V
Input Resistance	25°C		26		kΩ
Input Capacitance	25°C		5		pF
LOGIC OUTPUT (SDIO/PDWN) ³					
Logic 1 Voltage (I _{OH} = 800 μA)	Full		1.79		V
Logic 0 Voltage (I _{OL} = 50 μA)	Full			0.05	V
DIGITAL OUTPUTS (D0x±, D1x±), ANSI-644					
Logic Compliance			LVDS		
Differential Output Voltage Magnitude (V _{OD})	Full	290	345	400	mV
Output Offset Voltage (V _{OS})	Full	1.15	1.25	1.35	V
Output Offset Voltage (V _{OS}) W Grade	Full	1.12	1.25	1.35	V
Output Coding (Default)			Twos comple	ement	
DIGITAL OUTPUTS (D0x±, D1x±), LOW POWER, REDUCED SIGNAL OPTION					

analog.com Rev. C | 6 of 38

² Crosstalk is measured at 70 MHz with -1.0 dBFS analog input on one channel and no input on the adjacent channel.

³ Overrange condition is specified with 3 dB of the full-scale input range.

⁴ PSRR is measured by injecting a sinusoidal signal at 10 MHz to the power supply pin and measuring the output spur on the FFT. PSRR is calculated as the ratio of the amplitude of the spur voltage over the amplitude of the pin voltage, expressed in decibels (dB).

SPECIFICATIONS

Table 3. (Continued)

Parameter ¹	Temp	Min	Тур	Max	Unit
Logic Compliance			LVDS	'	
Differential Output Voltage Magnitude (V _{OD})	Full	160	200	230	mV
Output Offset Voltage (V _{OS})	Full	1.15	1.25	1.35	V
Output Offset Voltage (Vos) W Grade	Full	1.12	1.25	1.35	V
Output Coding (Default)			Twos compl	ement	

¹ See the AN-835 Application Note, Understanding High Speed ADC Testing and Evaluation, for definitions and for details on how these tests were completed.

SWITCHING SPECIFICATIONS

AVDD = 1.8 V, DRVDD = 1.8 V, 2 V p-p differential input, 1.0 V internal reference, AIN = -1.0 dBFS, unless otherwise noted.

Table 4.

Parameter ^{1, 2}	Temp	Min	Тур	Max	Unit
CLOCK ³					
Input Clock Rate	Full	10		1000	MHz
Conversion Rate ⁴	Full	10		80/125	MSPS
Clock Pulse Width High (t _{EH})	Full		6.25/4.00		ns
Clock Pulse Width Low (t _{EL})	Full		6.25/4.00		ns
OUTPUT PARAMETERS ³					
Propagation Delay (t _{PD})	Full	1.5	2.3	3.1	ns
Rise Time (t _R) (20% to 80%)	Full		300		ps
Fall Time (t _F) (20% to 80%)	Full		300		ps
FCO Propagation Delay (t _{FCO})	Full	1.5	2.3	3.1	ns
DCO Propagation Delay (t _{CPD}) ⁵	Full		$t_{FCO} + (t_{SAMPLE}/16)$		ns
DCO to Data Delay (t _{DATA}) ⁵	Full	(t _{SAMPLE} /16) - 300	t _{SAMPLE} /16	$(t_{SAMPLE}/16) + 300$	ps
DCO to FCO Delay (t _{FRAME}) ⁵	Full	(t _{SAMPLE} /16) - 300	t _{SAMPLE} /16	$(t_{SAMPLE}/16) + 300$	ps
Lane Delay (t _{LD})			90		ps
Data-to-Data Skew (t _{DATA-MAX} - t _{DATA-MIN})	Full		±50	±200	ps
Wake-Up Time (Standby)	25°C		250		ns
Wake-Up Time (Power-Down) ⁶	25°C		375		μs
Pipeline Latency	Full		16		Clock cycle
APERTURE					
Aperture Delay (t _A)	25°C		1		ns
Aperture Uncertainty (Jitter, t _J)	25°C		174		fs rms
Out-of-Range Recovery Time	25°C		1		Clock cycles

¹ See the AN-835 Application Note, Understanding High Speed ADC Testing and Evaluation, for definitions and for details on how these tests were completed.

analog.com Rev. C | 7 of 38

² Specified for LVDS and LVPECL only.

³ Specified for 13 SDIO/PDWN pins sharing the same connection.

² Measured on standard FR-4 material.

³ Can be adjusted via the SPI. The conversion rate is the clock rate after the divider.

⁴ The maximum conversion rate is based on two-lane output mode. See the Digital Outputs and Timing section for the maximum conversion rate in one-lane output mode.

 $^{^{5}}$ $t_{SAMPLE}/16$ is based on the number of bits in two LVDS data lanes. t_{SAMPLE} = 1/f_S.

⁶ Wake-up time is defined as the time required to return to normal operation from power-down mode.

SPECIFICATIONS

TIMING SPECIFICATIONS

Table 5.

Parameter	rameter Description			
SPI TIMING REQUIREMENTS	See Figure 70			
t_{DS}	Setup time between the data and the rising edge of SCLK	2	ns min	
t _{DH}	Hold time between the data and the rising edge of SCLK	2	ns min	
t _{CLK}	Period of the SCLK	40	ns min	
ts	Setup time between CSB and SCLK	2	ns min	
t _H	Hold time between CSB and SCLK	2	ns min	
t _{HIGH}	SCLK pulse width high	10	ns min	
t_{LOW}	SCLK pulse width low	10	ns min	
t _{en_sdio}	Time required for the SDIO pin to switch from an input to an output relative to the SCLK falling edge (not shown in Figure 70)	10	ns min	
t _{DIS_SDIO}	Time required for the SDIO pin to switch from an output to an input relative to the SCLK rising edge (not shown in Figure 70)	10	ns min	

TIMING DIAGRAMS

Refer to the Memory Map Register Descriptions section and Table 20 for SPI register settings.




Figure 2. 16-Bit DDR/SDR, Two-Lane, 1× Frame Mode (Default)

analog.com Rev. C | 8 of 38

SPECIFICATIONS




Figure 3. 12-Bit DDR/SDR, Two-Lane, 1× Frame Mode




Figure 4. 16-Bit DDR/SDR, Two-Lane, 2× Frame Mode

analog.com Rev. C | 9 of 38

SPECIFICATIONS




Figure 5. 12-Bit DDR/SDR, Two-Lane, 2× Frame Mode




Figure 6. Wordwise DDR, One-Lane, 1× Frame, 16-Bit Output Mode




Figure 7. Wordwise DDR, One-Lane, 1× Frame, 12-Bit Output Mode

analog.com Rev. C | 10 of 38

ABSOLUTE MAXIMUM RATINGS

Table 6.

Parameter	Rating
Electrical	
AVDD to AGND	-0.3 V to +2.0 V
DRVDD to AGND	-0.3 V to +2.0 V
Digital Outputs to AGND (D0x±, D1x±, DCO+, DCO-,FCO+, FCO-)	-0.3 V to +2.0 V
CLK+, CLK- to AGND	-0.3 V to +2.0 V
VINx+, VINx- to AGND	-0.3 V to +2.0 V
SCLK/DFS, SDIO/PDWN, CSB to AGND	-0.3 V to +2.0 V
RBIAS to AGND	-0.3 V to +2.0 V
VREF to AGND	-0.3 V to +2.0 V
VCM to AGND	-0.3 V to +2.0 V
Environmental	
Operating Temperature Range (Ambient)	-40°C to +85°C
Operating Temperature Range (Ambient) W Grade	-40°C to +105°C
Maximum Junction Temperature	150°C
Lead Temperature (Soldering, 10 sec)	300°C
Storage Temperature Range (Ambient)	-65°C to +150°C

Stresses at or above those listed under Absolute Maximum Ratings may cause permanent damage to the product. This is a stress rating only; functional operation of the product at these or any other conditions above those indicated in the operational section of this specification is not implied. Operation beyond the maximum operating conditions for extended periods may affect product reliability.

THERMAL RESISTANCE

The exposed paddle is the only ground connection on the chip. The exposed paddle must be soldered to the AGND plane of the user's circuit board. Soldering the exposed paddle to the user's board also increases the reliability of the solder joints and maximizes the thermal capability of the package.

Table 7. Thermal Resistance

Package Type	Airflow Velocity (m/sec)	θ _{JA} 1, 2	θ _{JC} ^{1, 3}	θ _{JB} ^{1, 4}	Ψ _{JT} 1, 2	Unit
32-Lead LFCSP, 5	0	37.1	3.1	20.7	0.3	°C/W
mm × 5 mm	1.0	32.4			0.5	°C/W
	2.5	29.1			0.8	°C/W

- ¹ Per JEDEC JESD51-7, plus JEDEC JESD51-5 2S2P test board.
- ² Per JEDEC JESD51-2 (still air) or JEDEC JESD51-6 (moving air).
- ³ Per MIL-STD 883, Method 1012.1.
- ⁴ Per JEDEC JESD51-8 (still air).

Typical θ_{JA} is specified for a 4-layer PCB with a solid ground plane. As shown in Table 7, airflow improves heat dissipation, which reduces θ_{JA} . In addition, metal in direct contact with the package leads from metal traces, through holes, ground, and power planes reduces the θ_{JA} .

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

analog.com Rev. C | 11 of 38

PIN CONFIGURATION AND FUNCTION DESCRIPTIONS




Figure 8. Pin Configuration, Top View

Table 8. Pin Function Descriptions

Pin No.	Mnemonic	Description
0	AGND, Exposed Pad	The exposed paddle is the only ground connection on the chip. It must be soldered to the analog ground of the PCB to ensure proper functionality and heat dissipation, noise, and mechanical strength benefits.
1, 24, 25, 28, 29, 32	AVDD	1.8 V Supply Pins for ADC Analog Core Domain.
2, 3	CLK+, CLK-	Differential Encode Clock for LVPECL, LVDS, or 1.8 V CMOS Inputs.
4	SDIO/PDWN	Data Input/Output in SPI Mode (SDIO). Bidirectional SPI data I/O with 30 k Ω internal pull-down. Power-Down in Non-SPI Mode (PDWN). Static control of chip power-down with 30 k Ω internal pull-down.
5	SCLK/DFS	SPI Clock Input in SPI Mode (SCLK). 30 k Ω internal pull-down. Data Format Select in Non-SPI Mode (DFS). Static control of data output format with 30 k Ω internal pull-down. DFS high = twos complement output; DFS low = offset binary output.
6, 19	DRVDD	1.8 V Supply Pins for Output Driver Domain.
7, 8	D1B-, D1B+	Channel B Digital Outputs.
9, 10	D0B-, D0B+	Channel B Digital Outputs.
11, 12	DCO-, DCO+	Data Clock Outputs.
13, 14	FCO-, FCO+	Frame Clock Outputs.
15, 16	D1A-, D1A+	Channel A Digital Outputs.
17, 18	D0A-, D0A+	Channel A Digital Outputs.
20	CSB	SPI Chip Select. Active low enable with 15 $k\Omega$ internal pull-up.
21	VREF	1.0 V Voltage Reference Output.
22	VCM	Analog Output Voltage at Mid AVDD Supply. Sets the common-mode voltage of the analog inputs.
23	RBIAS	Sets the analog current bias. Connect this pin to a 10 kΩ (1% tolerance) resistor to ground.
26, 27	VINA-, VINA+	Channel A ADC Analog Inputs.
30, 31	VINB+, VINB-	Channel B ADC Analog Inputs.

analog.com Rev. C | 12 of 38

TYPICAL PERFORMANCE CHARACTERISTICS

AD9645-80




Figure 9. Single-Tone 16k FFT with $f_{\rm IN}$ = 9.7 MHz, $f_{\rm SAMPLE}$ = 80 MSPS




Figure 10. Single-Tone 16k FFT with f_{IN} = 30.5 MHz, f_{SAMPLE} = 80 MSPS




Figure 11. Single-Tone 16k FFT with $f_{\rm IN}$ = 70.2 MHz, $f_{\rm SAMPLE}$ = 80 MSPS




Figure 12. Single-Tone 16k FFT with $f_{\rm IN}$ = 69.5 MHz, $f_{\rm SAMPLE}$ = 80 MSPS, Temp = -40 $^{\circ}$ C




Figure 13. Single-Tone 16k FFT with $f_{\rm IN}$ = 69.5 MHz, $f_{\rm SAMPLE}$ = 80 MSPS, Temp = 105 $^{\circ}$ C




Figure 14. Single-Tone 16k FFT with f_{IN} = 139.5 MHz, f_{SAMPLE} = 80 MSPS

analog.com Rev. C | 13 of 38

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 15. Single-Tone 16k FFT with f_{IN} = 200.5 MHz, f_{SAMPLE} = 80 MSPS




Figure 16. Single-Tone 16k FFT with $f_{\rm IN}$ = 200.5 MHz, $f_{\rm SAMPLE}$ = 80 MSPS, Clock Divide = Divide-by-8




Figure 17. SNR/SFDR vs. Analog Input Level; $f_{\rm IN}$ = 9.7 MHz, $f_{\rm SAMPLE}$ = 80 MSPS




Figure 18. Two-Tone 16k FFT with $f_{\rm IN1}$ = 70.5 MHz and $f_{\rm IN2}$ = 72.5 MHz, $f_{\rm SAMPLE}$ = 80 MSPS




Figure 19. Two-Tone SFDR/IMD3 vs. Input Amplitude (AIN) with $f_{\rm IN1}$ = 70.5 MHz and $f_{\rm IN2}$ = 72.5 MHz, $f_{\rm SAMPLE}$ = 80 MSPS




Figure 20. SNR/SFDR vs. f_{IN} ; $f_{SAMPLE} = 80$ MSPS

analog.com Rev. C | 14 of 38

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 21. SNR/SFDR vs. Temperature; f_{IN} = 9.7 MHz, f_{SAMPLE} = 80 MSPS




Figure 22. INL; $f_{IN} = 9.7 \text{ MHz}$, $f_{SAMPLE} = 80 \text{ MSPS}$




Figure 23. DNL; f_{IN} = 9.7 MHz, f_{SAMPLE} = 80 MSPS




Figure 24. Input Referred Noise Histogram; f_{SAMPLE} = 80 MSPS




Figure 25. PSRR vs. Frequency; $f_{CLK} = 125 \text{ MHz}$, $f_{SAMPLE} = 80 \text{ MSPS}$




Figure 26. SNR/SFDR vs. Sample Rate; f_{IN} = 9.7 MHz, f_{SAMPLE} = 80 MSPS

analog.com Rev. C | 15 of 38

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 27. SNR/SFDR vs. Sample Rate; f_{IN} = 70 MHz, f_{SAMPLE} = 80 MSPS

analog.com Rev. C | 16 of 38

TYPICAL PERFORMANCE CHARACTERISTICS

AD9645-125




Figure 28. Single-Tone 16k FFT with $f_{\rm IN}$ = 9.7 MHz, $f_{\rm SAMPLE}$ = 125 MSPS




Figure 29. Single-Tone 16k FFT with f_{IN} = 30.5 MHz, f_{SAMPLE} = 125 MSPS




Figure 30. Single-Tone 16k FFT with f_{IN} = 70.2 MHz, f_{SAMPLE} = 125 MSPS




Figure 31. Single-Tone 16k FFT with f_{IN} = 139.5 MHz, f_{SAMPLE} = 125 MSPS




Figure 32. Single-Tone 16k FFT with $f_{\rm IN}$ = 200.5 MHz, $f_{\rm SAMPLE}$ = 125 MSPS




Figure 33. Single-Tone 16k FFT with $f_{\rm IN}$ = 200.5 MHz, $f_{\rm SAMPLE}$ = 125 MSPS, Clock Divide = Divide-by-8

analog.com Rev. C | 17 of 38

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 34. SNR/SFDR vs. Analog Input Level; $f_{\rm IN}$ = 9.7 MHz, $f_{\rm SAMPLE}$ = 125 MSPS




Figure 35. Two-Tone 16k FFT with $f_{\rm IN1}$ = 70.5 MHz and $f_{\rm IN2}$ = 72.5 MHz, $f_{\rm SAMPLE}$ = 125 MSPS




Figure 36. Two-Tone SFDR/IMD3 vs. Input Amplitude (AIN) with $f_{\rm IN1}$ = 70.5 MHz and $f_{\rm IN2}$ = 72.5 MHz, $f_{\rm SAMPLE}$ = 125 MSPS




Figure 37. SNR/SFDR vs. f_{IN} ; $f_{SAMPLE} = 125 MSPS$




Figure 38. SNR/SFDR vs. Temperature; f_{IN} = 9.7 MHz, f_{SAMPLE} = 125 MSPS




Figure 39. INL; f_{IN} = 9.7 MHz, f_{SAMPLE} = 125 MSPS

analog.com Rev. C | 18 of 38

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 40. DNL; f_{IN} = 9.7 MHz, f_{SAMPLE} = 125 MSPS




Figure 41. Input Referred Noise Histogram; f_{SAMPLE} = 125 MSPS




Figure 42. PSRR vs. Frequency; f_{CLK} = 125 MHz, f_{SAMPLE} = 125 MSPS




Figure 43. SNR/SFDR vs. Sample Rate; f_{IN} = 9.7 MHz, f_{SAMPLE} = 125 MSPS




Figure 44. SNR/SFDR vs. Sample Rate; $f_{\rm IN}$ = 70 MHz, $f_{\rm SAMPLE}$ = 125 MSPS

analog.com Rev. C | 19 of 38

EQUIVALENT CIRCUITS




Figure 45. Equivalent Analog Input Circuit




Figure 46. Equivalent Clock Input Circuit




Figure 47. Equivalent SDIO/PDWN Input Circuit




Figure 48. Equivalent Digital Output Circuit




Figure 49. Equivalent SCLK/DFS Input Circuit




Figure 50. Equivalent RBIAS and VCM Circuit




Figure 51. Equivalent CSB Input Circuit




Figure 52. Equivalent VREF Circuit

analog.com Rev. C | 20 of 38

THEORY OF OPERATION

The AD9645 is a multistage, pipelined ADC. Each stage provides sufficient overlap to correct for flash errors in the preceding stage. The quantized outputs from each stage are combined into a final 14-bit result in the digital correction logic. The serializer transmits this converted data in a 16-bit output. The pipelined architecture permits the first stage to operate with a new input sample while the remaining stages operate with preceding samples. Sampling occurs on the rising edge of the clock.

Each stage of the pipeline, excluding the last, consists of a low resolution flash ADC connected to a switched-capacitor DAC and an interstage residue amplifier (for example, a multiplying digital-to-analog converter (MDAC)). The residue amplifier magnifies the difference between the reconstructed DAC output and the flash input for the next stage in the pipeline. One bit of redundancy is used in each stage to facilitate digital correction of flash errors. The last stage consists of a flash ADC.

The output staging block aligns the data, corrects errors, and passes the data to the output buffers. The data is then serialized and aligned to the frame and data clocks.

ANALOG INPUT CONSIDERATIONS

The analog input to the AD9645 is a differential switched-capacitor circuit designed for processing differential input signals. This circuit can support a wide common-mode range while maintaining excellent performance. By using an input common-mode voltage of midsupply, users can minimize signal-dependent errors and achieve optimum performance.




Figure 53. Switched-Capacitor Input Circuit

The clock signal alternately switches the input circuit between sample mode and hold mode (see Figure 53). When the input circuit is switched to sample mode, the signal source must be capable of charging the sample capacitors and settling within one-half of a clock cycle.

A small resistor in series with each input can help reduce the peak transient current injected from the output stage of the driving source. In addition, low Q inductors or ferrite beads can be placed on each leg of the input to reduce high differential capacitance at the analog inputs and, therefore, achieve the maximum bandwidth of the ADC. Such use of low Q inductors or ferrite beads is required

when driving the converter front end at high IF frequencies. Either a differential capacitor or two single-ended capacitors can be placed on the inputs to provide a matching passive network. This ultimately creates a low-pass filter at the input to limit unwanted broadband noise. See the AN-742 Application Note, the AN-827 Application Note, and the *Analog Dialogue* article "Transformer-Coupled Front-End for Wideband A/D Converters" (Volume 39, April 2005) for more information. In general, the precise values depend on the application.

INPUT COMMON MODE

The analog inputs of the AD9645 are not internally dc biased. Therefore, in ac-coupled applications, the user must provide this bias externally. Setting the device so that V_{CM} = AVDD/2 is recommended for optimum performance, but the device can function over a wider range with reasonable performance, as shown in Figure 54.




Figure 54. SNR/SFDR vs. Input Common-Mode Voltage, f_{IN} = 9.7 MHz, f_{SAMPLE} = 125 MSPS

An on-chip, common-mode voltage reference is included in the design and is available from the VCM pin. The VCM pin must be decoupled to ground by a 0.1 μ F capacitor, as described in the Applications Information section.

Maximum SNR performance is achieved by setting the ADC to the largest span in a differential configuration. In the case of the AD9645, the largest input span available is 2 V p-p.

DIFFERENTIAL INPUT CONFIGURATIONS

There are several ways to drive the AD9645 either actively or passively. However, optimum performance is achieved by driving the analog inputs differentially. Using a differential double balun configuration to drive the AD9645 provides excellent performance and a flexible interface to the ADC for baseband applications (see Figure 55).

For applications where SNR is a key parameter, differential transformer coupling is the recommended input configuration (see Figure 56) because the noise performance of most amplifiers is not adequate to achieve the true performance of the AD9645.

analog.com Rev. C | 21 of 38

THEORY OF OPERATION

Regardless of the configuration, the value of the shunt capacitor, C, is dependent on the input frequency and may need to be reduced or removed.

It is not recommended to drive the AD9645 inputs single-ended.




Figure 55. Differential Double Balun Input Configuration for Baseband Applications




Figure 56. Differential Transformer-Coupled Configuration for Baseband Applications

VOLTAGE REFERENCE

A stable and accurate 1.0 V voltage reference is built into the AD9645. The VREF pin should be externally decoupled to ground with a low ESR, 1.0 μF capacitor in parallel with a low ESR, 0.1 μF ceramic capacitor.

Figure 57 shows how the internal reference voltage is affected by loading. Figure 58 shows the typical drift characteristics of the internal reference in 1.0 V mode.

The internal buffer generates the positive and negative full-scale references for the ADC core.




Figure 57. V_{REF} Error vs. Load Current




Figure 58. Typical V_{REF} Drift

CLOCK INPUT CONSIDERATIONS

For optimum performance, clock the AD9645 sample clock inputs, CLK+ and CLK-, with a differential signal. The signal is typically ac-coupled into the CLK+ and CLK- pins via a transformer or capacitors. These pins are biased internally (see Figure 46) and require no external bias.

CLOCK INPUT OPTIONS

The AD9645 has a flexible clock input structure. The clock input can be a CMOS, LVDS, LVPECL, or sine wave signal. Regardless of the type of signal being used, clock source jitter is of the most concern, as described in the Jitter Considerations section.

Figure 59 and Figure 60 show two preferred methods for clocking the AD9645 (at clock rates up to 1 GHz prior to the internal clock divider). A low jitter clock source is converted from a single-ended signal to a differential signal using either an RF transformer or an RF balun.

analog.com Rev. C | 22 of 38

THEORY OF OPERATION




Figure 59. Transformer-Coupled Differential Clock (Up to 200 MHz)




Figure 60. Balun-Coupled Differential Clock (Up to 1 GHz)

The RF balun configuration is recommended for clock frequencies between 125 MHz and 1 GHz, and the RF transformer configuration is recommended for clock frequencies from 10 MHz to 200 MHz. The back-to-back Schottky diodes across the transformer/balun secondary winding limit clock excursions into the AD9645 to approximately 0.8 V p-p differential.

This limit helps prevent the large voltage swings of the clock from feeding through to other portions of the AD9645 while preserving the fast rise and fall times of the signal that are critical to achieving low jitter performance. However, the diode capacitance comes into play at frequencies above 500 MHz. Care must be taken when choosing the appropriate signal limiting diode.

If a low jitter clock source is not available, another option is to ac couple a differential PECL signal to the sample clock input pins, as shown in Figure 61. The AD9510/AD9511/AD9512/AD9513/AD9514/AD9515/AD9516-0/AD9516-1/AD9516-2/AD9516-3/AD9516-4/AD9516-5/AD9517-0/AD9517-1/AD9517-2/AD9517-3/AD9517-4 clock drivers offer excellent jitter performance.




Figure 61. Differential PECL Sample Clock (Up to 1 GHz)

A third option is to ac couple a differential LVDS signal to the sample clock input pins, as shown in Figure 62. The AD9510/AD9511/AD9512/AD9513/AD9514/AD9515/AD9516-0/AD9516-1/AD9516-2/AD9516-3/AD9516-4/AD9516-5/AD9517-0/

AD9517-1/AD9517-2/AD9517-3/AD9517-4 clock drivers offer excellent jitter performance.




Figure 62. Differential LVDS Sample Clock (Up to 1 GHz)

In some applications, it may be acceptable to drive the sample clock inputs with a single-ended 1.8 V CMOS signal. In such applications, drive the CLK+ pin directly from a CMOS gate, and bypass the CLK– pin to ground with a 0.1 μ F capacitor (see Figure 63).




Figure 63. Single-Ended 1.8 V CMOS Input Clock (Up to 200 MHz)

INPUT CLOCK DIVIDER

The AD9645 contains an input clock divider that can divide the input clock by integer values from 1 to 8. To achieve a given sample rate, the frequency of the externally applied clock must be multiplied by the divide value. The increased rate of the external clock normally results in lower clock jitter, which is beneficial for IF undersampling applications.

CLOCK DUTY CYCLE

Typical high speed ADCs use both clock edges to generate a variety of internal timing signals and, as a result, may be sensitive to the clock duty cycle. Commonly, a ±5% tolerance is required on the clock duty cycle to maintain dynamic performance characteristics.

The AD9645 contains a duty cycle stabilizer (DCS) that retimes the nonsampling (falling) edge, providing an internal clock signal with a nominal 50% duty cycle. This allows the user to provide a wide range of clock input duty cycles without affecting the performance of the AD9645. Noise and distortion performance are nearly flat for a wide range of duty cycles with the DCS on.

Jitter in the rising edge of the input is still of concern and is not easily reduced by the internal stabilization circuit. The duty cycle control loop does not function for clock rates of less than 20 MHz, nominally. The loop has a time constant associated with it that must be considered in applications in which the clock rate can

analog.com Rev. C | 23 of 38

THEORY OF OPERATION

change dynamically. A wait time of 1.5 μ s to 5 μ s is required after a dynamic clock frequency increase or decrease before the DCS loop is relocked to the input signal.

JITTER CONSIDERATIONS

High speed, high resolution ADCs are sensitive to the quality of the clock input. The degradation in SNR at a given input frequency (f_A) due only to aperture jitter (t_J) can be calculated by the following equation:

SNR Degradation =
$$20 \log_{10} \left(\frac{1}{2\pi \times f_A \times t_I} \right)$$

In this equation, the rms aperture jitter represents the root mean square of all jitter sources, including the clock input, analog input signal, and ADC aperture jitter specifications. IF undersampling applications are particularly sensitive to jitter (see Figure 64).




Figure 64. Ideal SNR vs. Input Frequency and Jitter

The clock input should be treated as an analog signal in cases where aperture jitter may affect the dynamic range of the AD9645. Power supplies for clock drivers should be separated from the ADC output driver supplies to avoid modulating the clock signal with digital noise. Low jitter, crystal-controlled oscillators make the best clock sources. If the clock is generated from another type of source (by gating, dividing, or other methods), it should be retimed by the original clock as the last step.

Refer to the AN-501 Application Note and the AN-756 Application Note for more in-depth information about jitter performance as it relates to ADCs.

POWER DISSIPATION AND POWER-DOWN MODE

As shown in Figure 65, the power dissipated by the AD9645 is proportional to its sample rate. The AD9645 is placed in power-down mode either by the SPI port or by asserting the PDWN pin high. In this state, the ADC typically dissipates 2 mW. During power-down, the output drivers are placed in a high impedance state. Asserting the PDWN pin low returns the AD9645 to its normal operating

mode. Note that PDWN is referenced to the digital output driver supply (DRVDD) and should not exceed that supply voltage.




Figure 65. Total Power Dissipation vs. f_{SAMPLE} for f_{IN} = 9.7 MHz

Low power dissipation in power-down mode is achieved by shutting down the reference, reference buffer, biasing networks, and clock. Internal capacitors are discharged when the part enters power-down mode and must then be recharged when the part returns to normal operation. As a result, wake-up time is related to the time spent in power-down mode, and shorter power-down cycles result in proportionally shorter wake-up times. When using the SPI port interface, the user can place the ADC in power-down mode or standby mode. Standby mode allows the user to keep the internal reference circuitry powered when faster wake-up times are required. See the Memory Map section for more details on using these features.

DIGITAL OUTPUTS AND TIMING

The AD9645 differential outputs conform to the ANSI-644 LVDS standard on default power-up. This default setting can be changed to a low power, reduced signal option (similar to the IEEE 1596.3 standard) via the SPI. The LVDS driver current is derived on chip and sets the output current at each output equal to a nominal 3.5 mA. A 100 Ω differential termination resistor placed at the LVDS receiver inputs results in a nominal 350 mV swing (or 700 mV p-p differential) at the receiver.

When operating in reduced range mode, the output current is reduced to 2 mA. This results in a 200 mV swing (or 400 mV p-p differential) across a 100 Ω termination at the receiver.

The LVDS outputs facilitate interfacing with LVDS receivers in custom ASICs and FPGAs for superior switching performance in noisy environments. Single point-to-point net topologies are recommended with a 100 Ω termination resistor placed as close as possible to the receiver. If there is no far-end receiver termination or there is poor differential trace routing, timing errors may result. To avoid such timing errors, ensure that the trace length is less than 24 inches and that the differential output traces are close together and at equal lengths.

analog.com Rev. C | 24 of 38

THEORY OF OPERATION

Figure 66 shows an example of the FCO and data stream with proper trace length and position.




Figure 66. AD9645-125, LVDS Output Timing Example in ANSI-644 Mode (Default)

Figure 67 shows the LVDS output timing example in reduced range mode.




Figure 67. AD9645-125, LVDS Output Timing Example in Reduced Range Mode

Figure 68 shows an example of the LVDS output using the AN-SI-644 standard (default) data eye and a time interval error (TIE) jitter histogram with trace lengths of less than 24 inches on standard FR-4 material.




Figure 68. Data Eye for LVDS Outputs in ANSI-644 Mode with Trace Lengths of Less Than 24 Inches on Standard FR-4 Material, External 100 Ω Far-End Termination Only

Figure 69 shows an example of trace lengths exceeding 24 inches on standard FR-4 material. Note that the TIE jitter histogram reflects the decrease of the data eye opening as the edge deviates from the ideal position.




Figure 69. Data Eye for LVDS Outputs in ANSI-644 Mode with Trace Lengths Greater Than 24 Inches on Standard FR-4 Material, External 100 Ω Far-End Termination Only

It is the responsibility of the user to determine if the waveforms meet the timing budget of the design when the trace lengths exceed 24 inches. Additional SPI options allow the user to further increase the internal termination (increasing the current) of both outputs to drive longer trace lengths. This increase in current can be achieved by programming Register 0x15. Although an increase

in current produces sharper rise and fall times on the data edges and is less prone to bit errors, the power dissipation of the DRVDD supply increases when this option is used.

The format of the output data is two complement by default. An example of the output coding format can be found in Table 9. To

analog.com Rev. C | 25 of 38

THEORY OF OPERATION

change the output data format to offset binary, see the Memory Map section.

Data from each ADC is serialized and provided on a separate channel in two lanes in DDR mode. The data rate for each serial stream is equal to (16 bits × the sample clock rate)/2 lanes, with a maximum of 1 Gbps/lane ((16 bits × 125 MSPS)/(2 lanes) = 1 Gbps/lane)). The maximum allowable output data rate is 1 Gbps/lane. If one-lane mode is used, the data rate doubles for a given sample rate. To stay within the maximum data rate of 1 Gbps/lane, the sample rate is limited to a maximum of 62.5 MSPS in one-lane output mode.

The lowest typical conversion rate is 10 MSPS. For conversion rates of less than 20 MSPS, the SPI must be used to reconfigure the integrated PLL. See Register 0x21 in the Memory Map section for details on enabling this feature.

Two output clocks are provided to assist in capturing data from the AD9645. The DCO is used to clock the output data and is equal to 4× the sample clock (CLK) rate for the default mode of operation. Data is clocked out of the AD9645 and must be captured on the

rising and falling edges of the DCO that supports double data rate (DDR) capturing. The FCO is used to signal the start of a new output byte and is equal to the sample clock rate in 1× frame mode. See the Timing Diagrams section for more information.

When the SPI is used, the DCO phase can be adjusted in 60° increments relative to the data edge. This enables the user to refine system timing margins, if required. The default DCO+ and DCO-timing, as shown in Figure 2, is 180° relative to the output data edge.

A 12-bit serial stream can also be initiated from the SPI. This allows the user to implement and test compatibility to lower resolution systems. When changing the resolution to a 12-bit serial stream, the data stream is shortened. See Figure 3 for the 12-bit example. In the default option with the serial output number of bits at 16, the data stream stuffs two 0s at the end of the 14-bit serial data.

In default mode, as shown in Figure 2, the MSB is first in the data output serial stream. This can be inverted by using the SPI so that the LSB is first in the data output serial stream.

Table 9. Digital Output Coding

Input (V)	Condition (V)	Offset Binary Output Mode	Twos Complement Mode	
VIN+ - VIN-	<-VREF - 0.5 LSB	0000 0000 0000 0000	1000 0000 0000 0000	
VIN+ - VIN-	-VREF	0000 0000 0000 0000	1000 0000 0000 0000	
VIN+ - VIN-	0 V	1000 0000 0000 0000	0000 0000 0000 0000	
VIN+ - VIN-	+VREF - 1.0 LSB	1111 1111 1111 1100	0111 1111 1111 1100	
VIN+ - VIN-	>+VREF - 0.5 LSB	1111 1111 1111 1100	0111 1111 1111 1100	

Table 10. Flexible Output Test Modes

Output Test Mode Bit Sequence	Pattern Name Digital Output Word 1		Digital Output Word 2	Subject to Data Format Select	Notes
0000	Off (default)	Not applicable	Not applicable	N/A	
0001	Midscale short	1000 0000 0000 (12-bit) 1000 0000 0000 0000 (16-bit)	Not applicable	Yes	Offset binary code shown
0010	+Full-scale short	1111 1111 1111 (12-bit) 1111 1111 1111 1100 (16-bit)	Not applicable	Yes	Offset binary code shown
0011	-Full-scale short	0000 0000 0000 (12-bit) 0000 0000 0000 0000 (16-bit)	Not applicable	Yes	Offset binary code shown
0100	Checkerboard	1010 1010 1010 (12-bit) 1010 1010 1010 1000 (16-bit)	0101 0101 0101 (12-bit) 0101 0101 0101 0100 (16-bit)	No	
0110	PN sequence short ¹	Not applicable	Not applicable	Yes	PN9 ITU 0.150 X ⁹ + X ⁵ + 1
0111	One-/zero-word toggle	1111 1111 1111 (12-bit) 111 1111 1111 1100 (16-bit)	0000 0000 0000 (12-bit) 0000 0000 0000 0000 (16-bit)	No	
1000	User input	Register 0x19 and Register 0x1A	Register 0x1B and Register 0x1C	No	
1001	1-/0-bit toggle	1010 1010 1010 (12-bit) 1010 1010 1010 1000 (16-bit)	Not applicable	No	
1010	1× sync	0000 0011 1111 (12-bit) 0000 0001 1111 1100 (16-bit)	Not applicable	No	
1011	11 One bit high 1000 0000 0000 (12-bit) 1000 0000 0000 0000 (16-bit)		Not applicable	No	Pattern associated with the external pin

analog.com Rev. C | 26 of 38

THEORY OF OPERATION

Table 10. Flexible Output Test Modes (Continued)

Output Test Mode Bit Sequence Pattern Name Digital Output Word 1		Digital Output Word 2	Subject to Data Format Select	Notes	
1100	Mixed frequency	1010 0011 0011 (12-bit) 1010 0001 1001 1100 (16-bit)	Not applicable	No	

¹ All test mode options except PN sequence short can support 12-bit to 16-bit word lengths to verify data capture to the receiver.

There are 11 digital output test pattern options available that can be initiated through the SPI. This is a useful feature when validating receiver capture and timing. Refer to Table 10 for the output bit sequencing options available. Some test patterns have two serial sequential words and can be alternated in various ways, depending on the test pattern chosen.

Note that some patterns do not adhere to the data format select option. In addition, custom user-defined test patterns can be assigned in the 0x19, 0x1A, 0x1B, and 0x1C register addresses.

The PN sequence short pattern produces a pseudorandom bit sequence that repeats itself every 2^9 – 1 or 511 bits. A description of the PN sequence and how it is generated can be found in Section 5.1 of the ITU-T 0.150 (05/96) standard. The seed value is all 1s (see Table 11 for the initial values). The output is a parallel representation of the serial PN9 sequence in MSB-first format. The first output word is the first 14 bits of the PN9 sequence in MSB aligned form.

Table 11. PN Sequence

Sequence	Initial Value	Next Three Output Samples (MSB First), Twos Complement
PN Sequence Short	0x1FE0	0x1DF1, 0x3CC8, 0x294E

Consult the Memory Map section for information on how to change these additional digital output timing features through the SPI.

SDIO/PDWN PIN

For applications that do not require SPI mode operation, the CSB pin is tied to DRVDD, and the SDIO/PDWN pin controls power-down mode according to Table 12.

Table 12. Power-Down Mode Pin Settings

PDWN Pin Voltage	Device Mode
AGND (Default)	Run device, normal operation
DRVDD	Power down device

Note that in non-SPI mode (CSB tied to DRVDD), the power-up sequence described in the Power and Ground Guidelines section must be adhered to. Violating the power-up sequence necessitates a soft reset via the SPI, which is not possible in non-SPI mode.

SCLK/DFS PIN

The SCLK/DFS pin is used for output format selection in applications that do not require SPI mode operation. This pin determines the digital output format when the CSB pin is held high during device power-up. When SCLK/DFS is tied to DRVDD, the ADC

output format is twos complement; when SCLK/DFS is tied to AGND, the ADC output format is offset binary.

Table 13. Digital Output Format

DFS Voltage	Output Format
AGND	Offset binary
DRVDD	Twos complement

CSB PIN

The CSB pin should be tied to DRVDD for applications that do not require SPI mode operation. By tying CSB high, all SCLK and SDIO information is ignored.

Note that, in non-SPI mode (CSB tied to DRVDD), the power-up sequence described in the Power and Ground Guidelines section must be adhered to. Violating the power-up sequence necessitates a soft reset via SPI, which is not possible in non-SPI mode.

RBIAS PIN

To set the internal core bias current of the ADC, place a 10.0 k Ω , 1% tolerance resistor to ground at the RBIAS pin.

OUTPUT TEST MODES

The output test options are described in Table 10 and are controlled by the output test mode bits at Address 0x0D. When an output test mode is enabled, the analog section of the ADC is disconnected from the digital back-end blocks and the test pattern is run through the output formatting block. Some of the test patterns are subject to output formatting, and some are not. The PN generators from the PN sequence tests can be reset by setting Bit 4 of Register 0x0D. These tests can be performed with or without an analog signal (if present, the analog signal is ignored), but they do require an encode clock. For more information, see the AN-877 Application Note, Interfacing to High Speed ADCs via SPI.

Data from the output test modes are not necessarily time aligned from channel to channel. In cases where the output test mode data are not aligned across all channels, data alignment is restored when the output test mode bits are disabled and data from the ADC cores are transmitted in normal functional mode (Register 0x0D = 0x00).

analog.com Rev. C | 27 of 38

SERIAL PORT INTERFACE (SPI)

The AD9645 serial port interface (SPI) allows the user to configure the converter for specific functions or operations through a structured register space provided inside the ADC. The SPI offers the user added flexibility and customization, depending on the application. Addresses are accessed via the serial port and can be written to or read from via the port. Memory is organized into bytes that can be further divided into fields, which are documented in the Memory Map section. For general operational information, see the AN-877 Application Note, *Interfacing to High Speed ADCs via SPI*.

CONFIGURATION USING THE SPI

Three pins define the SPI of this ADC: the SCLK/DFS pin, the SDIO/PDWN pin, and the CSB pin (see Table 14). SCLK/DFS (a serial clock when CSB is low) is used to synchronize the read and write data presented from and to the ADC. SDIO/PDWN (serial data input/output when CSB is low) is a dual-purpose pin that allows data to be sent to and read from the internal ADC memory map registers. CSB (chip select bar) is an active low control that enables or disables the SPI read and write cycles.

Table 14. Serial Port Interface Pins

Pin	Function
SCLK/DFS	Serial clock when CSB is low. The serial shift clock input, which is used to synchronize serial interface reads and writes.
SDIO/PDWN	Serial data input/output when CSB is low. A dual-purpose pin that typically serves as an input or an output, depending on the instruction being sent and the relative position in the timing frame.
CSB	Chip select bar. An active low control that enables the SPI mode read and write cycles.

The falling edge of CSB, in conjunction with the rising edge of SCLK/DFS, determines the start of the framing. An example of the serial timing is shown in Figure 70. See Table 5 for definitions of the timing parameters.

Other modes involving the CSB pin are available. CSB can be held low indefinitely, which permanently enables the device; this is called streaming. CSB can stall high between bytes to allow for additional external timing. When the CSB pin is tied high, SPI functions are placed in high impedance mode. This mode turns on the secondary functions of the SPI pins.

During the instruction phase of a SPI operation, a 16-bit instruction is transmitted. Data follows the instruction phase, and its length is determined by the W0 and W1 bits.

In addition to word length, the instruction phase determines whether the serial frame is a read or write operation, allowing the serial port to be used both to program the chip and to read the contents of the on-chip memory. The first bit of the first byte in a multibyte serial data transfer frame indicates whether a read command or a write command is issued. If the instruction is a readback operation, performing a readback causes the serial data input/output (SDIO) pin to change direction from an input to an output at the appropriate point in the serial frame.

All data is composed of 8-bit words. Data can be sent in MSB-first mode or in LSB-first mode. MSB-first mode is the default on power-up and can be changed via the SPI port configuration register. For more information about this and other features, see the AN-877 Application Note, *Interfacing to High Speed ADCs via SPI*.




Figure 70. Serial Port Interface Timing Diagram

analog.com Rev. C | 28 of 38

SERIAL PORT INTERFACE (SPI)

HARDWARE INTERFACE

The pins described in Table 14 comprise the physical interface between the user programming device and the serial port of the AD9645. The SCLK/DFS pin and the CSB pin function as inputs when using the SPI interface. The SDIO/PDWN pin is bidirectional, functioning as an input during write phases and as an output during readback.

The SPI interface is flexible enough to be controlled by either FPGAs or microcontrollers. One method for SPI configuration is described in detail in the AN-812 Application Note, *Microcontroller-Based Serial Port Interface (SPI) Boot Circuit*.

The SPI port should not be active during periods when the full dynamic performance of the converter is required. Because the SCLK/DFS signal, the CSB signal, and the SDIO/PDWN signal are typically asynchronous to the ADC clock, noise from these signals can degrade converter performance. If the on-board SPI bus is used for other devices, it may be necessary to provide buffers between this bus and the AD9645 to prevent these signals from transitioning at the converter inputs during critical sampling periods.

The SCLK/DFS and SDIO/PDWN pins serve a dual function when the SPI interface is not being used. When the pins are strapped to DRVDD or ground during device power-on, they are associated with a specific function. Table 12 and Table 13 describe the strappable functions supported on the AD9645.

CONFIGURATION WITHOUT THE SPI

In applications that do not interface to the SPI control registers, the SCLK/DFS pin and the SDIO/PDWN pin serve as standalone CMOS-compatible control pins. When the device is powered up, it

is assumed that the user intends to use the pins as static control lines for the output data format and power-down feature control. In this mode, CSB should be connected to DRVDD, which disables the serial port interface.

Note that, in non-SPI mode (CSB tied to DRVDD), the power-up sequence described in the Power and Ground Guidelines section must be adhered to. Violating the power-up sequence necessitates a soft reset via the SPI, which is not possible in non-SPI mode.

SPI ACCESSIBLE FEATURES

Table 15 provides a brief description of the general features that are accessible via the SPI. These features are described in general in the AN-877 Application Note, *Interfacing to High Speed ADCs via SPI*. The AD9645 part-specific features are described in detail in Table 16, the external memory map register table and the following text.

Table 15. Features Accessible Using the SPI

Feature Name	Description
Power Mode	Allows the user to set either power-down mode or standby mode
Clock	Allows the user to access the DCS, set the clock divider, and set the clock divider phase
Offset	Allows the user to digitally adjust the converter offset
Test I/O	Allows the user to set test modes to have known data on output bits
Output Mode	Allows the user to set the output mode
Output Phase	Allows the user to set the output clock polarity
ADC Resolution	Allows for power consumption scaling with respect to sample rate

analog.com Rev. C | 29 of 38

MEMORY MAP

READING THE MEMORY MAP REGISTER TABLE

Each row in the memory map register table (see Table 16) has eight bit locations. The memory map is roughly divided into three sections: the chip configuration registers (Address 0x00 to Address 0x02); the device index and transfer registers (Address 0x05 and Address 0xFF); and the global ADC function registers, including setup, control, and test (Address 0x08 to Address 0x102).

The memory map register table lists the default hexadecimal value for each hexadecimal address shown. The column with the heading Bit 7 (MSB) is the start of the default hexadecimal value given. For example, Address 0x05, the device index register, has a hexadecimal default value of 0x33. This means that in Address 0x05, Bits[7:6] = 00, Bits[5:4] = 11, Bits[3:2] = 00, and Bits[1:0] = 11 (in binary). This setting is the default channel index setting. The default value results in both ADC channels receiving the next write command. For more information on this function and others, see the AN-877 Application Note, *Interfacing to High Speed ADCs via SPI*. This application note details the functions controlled by Register 0x00 to Register 0xFF. The remaining registers are documented in the Memory Map Register Descriptions section.

OPEN LOCATIONS

All address and bit locations that are not included in Table 16 are not currently supported for this device. Unused bits of a valid address location should be written with 0s. Writing to these locations is required only when part of an address location is open (for example, Address 0x05). If the entire address location is open or not listed in Table 16 (for example, Address 0x13), this address location should not be written.

DEFAULT VALUES

After the AD9645 is reset, critical registers are loaded with default values. The default values for the registers are given in the memory map register table, Table 16.

LOGIC LEVELS

An explanation of logic level terminology follows:

- ▶ "Bit is set" is synonymous with "bit is set to Logic 1" or "writing Logic 1 for the bit."
- ► "Clear a bit" is synonymous with "bit is set to Logic 0" or "writing Logic 0 for the bit."

CHANNEL-SPECIFIC REGISTERS

Some channel setup functions can be programmed differently for each channel. In these cases, channel address locations are internally duplicated for each channel. These registers and bits are designated in Table 16 as local. These local registers and bits can be accessed by setting the appropriate data channel bits (A or B) and the clock channel DCO bit (Bit 5) and FCO bit (Bit 4) in Register 0x05. If all the bits are set, the subsequent write affects

the registers of both channels and the DCO/FCO clock channels. In a read cycle, only one channel (A or B) should be set to read one of the two registers. If all the bits are set during a SPI read cycle, the part returns the value for Channel A. Registers and bits that are designated as global in Table 16 affect the entire part or the channel features for which independent settings are not allowed between channels. The settings in Register 0x05 do not affect the global registers and bits.

analog.com Rev. C | 30 of 38

MEMORY MAP

MEMORY MAP REGISTER TABLE

The AD9645 uses a 3-wire interface and 16-bit addressing and, therefore, Bit 0 and Bit 7 in Register 0x00 are set to 0, and Bit 3 and Bit 4 are set to 1.

When Bit 5 in Register 0x00 is set high, the SPI enters a soft reset, where all of the user registers revert to their default values and Bit 2 is automatically cleared.

Table 16.

Addr. (Hex)	Parameter Name	Bit 7 (MSB)	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0(LSB)	Default Value (Hex)	Comments
	onfiguration Registers	21t : (III-02)		20	2	2	2.1.2	2	2.0 (202)	(Hex)	
0x00	SPI port configuration	0 = SDO active	LSB first	Soft reset	1 = 16-bit address	1 = 16-bit address	Soft reset	LSB first	0 = SDO active	0x18	Nibbles are mirrored to allow a given register value to perform the same function for either MSB-first or LSB-first mode.
0x01	Chip ID (global)		AD964	45 0x8B = du	8-bit chip IE al, 14-bit, 80		SPS, serial LV	/DS		0x8B	Unique chip ID used to differentiate devices; read only.
0x02	Chip grade (global)	Open	100	rade ID, Bits[= 80 MSPS = 125 MSPS	-	Open	Open	Open	Open		Unique speed grade ID used to differentiate graded devices; read only.
Device	Index and Transfer Re	egisters	1								
0x05	Device index	Open	Open	Clock Channel DCO	Clock Channel FCO	Open	Open	Data Channel B	Data Channel A	0x33	Bits are set to determine which device on chip receives the next write command. Default is all devices on chip.
0xFF	Transfer	Open	Open	Open	Open	Open	Open	Open	Initiate override	0x00	Set resolution/ sample rate override.
Global A	ADC Function Registe	ers							-		'
0x08	Power modes (global)	Open	Open	Open	Open	Open	Open	Power mode 00 = chip run 01 = full power-down 10 = standby 11 = reset		0x00	Determines various generic modes of chip operation.
0x09	Clock (global)	Open	Open	Open	Open	Open	Open	Open	Duty cycle stabilizer 0 = off 1 = on	0x00	Turns duty cycle stabilizer on or off.
0x0B	Clock divide (global)	Open	Open	Open	Open	Open		ock divide rati 000 = divide t 001 = divide t 010 = divide t 011 = divide t 100 = divide t	oy 1 oy 2 oy 3 oy 4	0x00	

analog.com Rev. C | 31 of 38

MEMORY MAP

Table 16. (Continued)

Addr. (Hex)	Parameter Name	Bit 7 (MSB)	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0(LSB)	Default Value (Hex)	Comments
(HOA)	- Granicion Hamile							101 = divide by 6 110 = divide by 7 111 = divide by 8			
0x0C	Enhancement control	Open	Open	Open	Open	Open	Chop mode 0 = off 1 = on	Open	Open	0x00	Enables/ disables chop mode.
0x0D	Test mode (local except for PN sequence resets)	00 01 = 10 = : 11 = al (affects use	put test mode = single = alternate single once ternate once er input test mode s[3:0] = 1000)	Open	Reset PN short gen		0001 = m 0010 = 0011 = I 0100 = alterna 0100 0110 = P 0111 = one-/: 1000 = 1001 = 1 1010 1011 = 0	off (default) nidscale short positive FS negative FS	pard	0x00	When set, the test data is placed on the output pins in place of normal data.
0x10	Offset adjust (local)		8-bit device offset adjustment, Bits[7:0] (local) Offset adjust in LSBs from +127 to −128 (twos complement format)					0x00	Device offset trim.		
0x14	Output mode	Open	LVDS-ANSI/ LVDS-IEEE option 0 = LVDS-ANSI 1 = LVDS-IEEE reduced range link (global); see Table 17	Open	Open	Open	Output invert (local)	Open	Output format 0 = offset binary 1 = twos complement (global)	0x01	Configures the outputs and format of the data.
0x15	Output adjust	Open	Open	terminatio 00 = 01 = 10 =	t driver n, Bits[1:0] none 200 Ω 100 Ω	Open	Open	Open	Output drive 0 = 1× drive 1 = 2× drive	0x00	Determines LVDS or other output properties.
0x16	Output phase	Open	Input clock p (value is numbe phase del	hase adjust, l	Bits[6:4] ck cycles of		Output clock ph (0000 through		0x03	On devices using global clock divide, determines which phase of the divider output is used to supply the output clock. Internal latching is unaffected.	
0x18	V _{REF}	Open	Open	Open	Open	Open Internal V _{REF} adjustment digital scheme, Bits[2:0] 000 = 1.0 V p-p 001 = 1.14 V p-p 010 = 1.33 V p-p 011 = 1.6 V p-p		0x04	Selects and/or adjusts V _{REF} .		

analog.com Rev. C | 32 of 38

MEMORY MAP

Table 16. (Continued)

Addr. (Hex)	Parameter Name	Bit 7 (MSB)	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0(LSB)	Default Value (Hex)	Comments
. ,		, ,						100 = 2.0 V	D-p		
0x19	USER_PATT1_LS B (global)	B7	B6	B5	B4	В3	B2	B1	B0	0x00	User Defined Pattern 1 LSB.
0x1A	USER_PATT1_M SB (global)	B15	B14	B13	B12	B11	B10	B9	B8	0x00	User Defined Pattern 1 MSB.
0x1B	USER_PATT2_LS B (global)	B7	B6	B5	B4	В3	B2	B1	В0	0x00	User Defined Pattern 2 LSB.
0x1C	USER_PATT2_M SB (global)	B15	B14	B13	B12	B11	B10	B9	B8	0x00	User Defined Pattern 2 MSB.
0x21	Serial output data control (global)	LVDS output 0 = MSB first (default) 1 = LSB first	SDR/DDR one-lane/two-lane, bitwise/byte-wise, Bits[6:4] 000 = SDR two-lane, bitwise 001 = SDR two-lane, bytewise 010 = DDR two-lane, bitwise 011 = DDR two-lane, bytewise (default) 100 = DDR one-lane, wordwise			Encode mode 0 = normal encode rate mode (default) 1 = low encode mode for sample rate of <20 MSPS	0 = 1× frame (default) 1 = 2× frame	00 = 16	out number of bits bits (default) : 12 bits	0x30	Serial stream control.Sample rate of <20 MSPS requires that Bits[6:4] = 100 (DDR onelane) and Bit 3 = 1 (low encode mode).
0x22	Serial channel status (local)	Open	Open	Open	Open	Open	Open	Channel output reset	Channel power-down	0x00	Used to power down individual sections of a converter.
0x100	Resolution/ sample rate override	Open	Resolution/ sample rate override enable	Resolution 01 = 14 bits 10 = 12 bits		Open	Sample rate 000 = 20 MSPSv 001 = 40 MSPS 010 = 50 MSPS 011 = 65 MSPS 100 = 80 MSPS 101 = 105 MSPS 110 = 125 MSPS		PSV PS PS PS PS SPS	0x00	Resolution/ sample rate override (requires writing to the transfer register, 0xFF).
0x101	User I/O Control 2	Open	Open	Open	Open	Open	Open	Open	SDIO pull-down	0x00	Disables SDIO pull-down.
0x102	User I/O Control 3	Open	Open	Open	Open	VCM power- down	Open	Open	Open	0x00	VCM control.

MEMORY MAP REGISTER DESCRIPTIONS

For additional information about functions controlled in Register 0x00 to Register 0xFF, see the AN-877 Application Note, *Interfacing to High Speed ADCs via SPI*.

DEVICE INDEX (REGISTER 0X05)

There are certain features in the map that can be set independently for each channel, whereas other features apply globally to all channels (depending on context), regardless of which is selected. Bits[1:0] in Register 0x05 can be used to select which individual data channel is affected. The output clock channels can be selected

in Register 0x05, as well. A smaller subset of the independent feature list can be applied to those devices.

TRANSFER (REGISTER 0XFF)

All registers except Register 0x100 are updated the moment they are written. Setting Bit 0 of Register 0xFF high initializes the settings in the ADC sample rate override register (Address 0x100).

analog.com Rev. C | 33 of 38

MEMORY MAP

POWER MODES (REGISTER 0X08)

Bits[7:2]—Open

Bits[1:0]—Power Mode

In normal operation (Bits[1:0] = 00), both ADC channels are active.

In power-down mode (Bits[1:0] = 01), the digital datapath clocks are disabled while the digital datapath is reset. Outputs are disabled.

In standby mode (Bits[1:0] = 10), the digital datapath clocks and the outputs are disabled.

During a digital reset (Bits[1:0] = 11), all the digital datapath clocks and the outputs (where applicable) on the chip are reset, except the SPI port. Note that the SPI is always left under control of the user; that is, it is never automatically disabled or in reset (except by power-on reset).

ENHANCEMENT CONTROL (REGISTER 0X0C)

Bits[7:3]—Open

Bit 2—Chop Mode

For applications that are sensitive to offset voltages and other low frequency noise, such as homodyne or direct conversion receivers, chopping in the first stage of the AD9645 is a feature that can be enabled by setting Bit 2. In the frequency domain, chopping translates offsets and other low frequency noise to $f_{CLK}/2$, where it can be filtered.

Bits[1:0]—Open

OUTPUT MODE (REGISTER 0X14)

Bit 7—Open

Bit 6—LVDS-ANSI/LVDS-IEEE Option

Setting this bit selects the LVDS-IEEE (reduced range) option.

The default setting is LVDS-ANSI. When LVDS-ANSI or the LVDS-IEEE reduced range link is selected, the user can select the driver termination (see Table 17). The driver current is automatically selected to give the proper output swing.

Table 17. LVDS-ANSI/LVDS-IEEE Options

Output Mode, Bit 6	Output Mode	Output Driver Termination	Output Driver Current			
0	LVDS-ANSI	User selectable	Automatically selected to give proper swing			
1	LVDS-IEEE reduced range link	User selectable	Automatically selected to give proper swing			

Bits[5:3]—Open

Bit 2—Output Invert

Setting this bit inverts the output bit stream.

Bit 1—Open

Bit 0—Output Format

By default, this bit is set to send the data output in twos complement format. Clearing this bit to 0 changes the output mode to offset binary.

OUTPUT ADJUST (REGISTER 0X15)

Bits[7:6]—Open

Bits[5:4]—Output Driver Termination

These bits allow the user to select the internal termination resistor.

Bits[3:1]—Open

Bit 0—Output Drive

Bit 0 of the output adjust register controls the drive strength on the LVDS driver of the FCO and DCO outputs only. The default values set the drive to 1×, or the drive can be increased to 2× by setting the appropriate channel bit in Register 0x05 and then setting Bit 0. These features cannot be used with the output driver termination select. The termination selection takes precedence over the 2× driver strength on FCO and DCO when both the output driver termination and output drive are selected.

OUTPUT PHASE (REGISTER 0X16)

Bit 7—Open

Bits[6:4]—Input Clock Phase Adjust

When the clock divider (Register 0x0B) is used, the applied clock is at a higher frequency than the internal sampling clock. Bits[6:4] determine at which phase of the external clock sampling occurs. This is only applicable when the clock divider is used. Setting Bits[6:4] greater than Register 0x0B, Bits[2:0] is prohibited.

Table 18. Input Clock Phase Adjust Options

Input Clock Phase Adjust, Bits[6:4]	Number of Input Clock Cycles of Phase Delay
000 (Default)	0
001	1
010	2
011	3
100	4
101	5
110	6

analog.com Rev. C | 34 of 38

MEMORY MAP

Table 18. Input Clock Phase Adjust Options (Continued)

Input Clock Phase Adjust,	Number of Input Clock Cycles of Phase
Bits[6:4]	Delay
111	7

Bits[3:0]—Output Clock Phase Adjust

See Table 19 for details.

Table 19. Output Clock Phase Adjust Options

Output Clock (DCO), Phase	DCO Phase Adjustment (Degrees Relative to		
Adjust, Bits[3:0]	D0x±/D1x± Edge)		
0000	0		
0001	60		
0010	120		
0011 (Default)	180		
0100	240		
0101	300		
0110	360		
0111	420		
1000	480		
1001	540		
1010	600		
1011	660		

SERIAL OUTPUT DATA CONTROL (REGISTER 0X21)

The serial output data control register is used to program the AD9645 in various output data modes, depending on the data capture solution. Table 20 describes the various serialization options available in the AD9645.

Table 20. SPI Register Options

RESOLUTION/SAMPLE RATE OVERRIDE (REGISTER 0X100)

This register allows the user to downgrade the resolution and/or the maximum sample rate (for lower power) in applications that do not require full resolution and/or sample rate. Settings in this register are not initialized until Bit 0 of the transfer register (Register 0xFF) is written high.

Bits[2:0] do not affect the sample rate; they affect the maximum sample rate capability of the ADC.

USER I/O CONTROL 2 (REGISTER 0X101)

Bits[7:1]—Open

Bit 0—SDIO Pull-Down

Bit 0 can be set to disable the internal 30 k Ω pull-down on the SDIO pin, which can be used to limit the loading when many devices are connected to the SPI bus.

USER I/O CONTROL 3 (REGISTER 0X102)

Bits[7:4]—Open

Bit 3—VCM Power-Down

Bit 3 can be set high to power down the internal VCM generator. This feature is used when applying an input common mode voltage from an external source.

Bits[2:0]—Open

Serialization Options Selected						
Register 0x21 Serial Output Number of Contents Bits (SONB)		Frame Mode Serial Data Mode		DCO Multiplier	Timing Diagram	
0x30	16-bit	1×	DDR two-lane bytewise	4 × f _S	See Figure 2 (default setting)	
0x20	16-bit	1×	DDR two-lane bitwise	4 × f _S	See Figure 2	
0x10	16-bit	1×	SDR two-lane bytewise	8 × f _S	See Figure 2	
0x00	16-bit	1×	SDR two-lane bitwise	8 × f _S	See Figure 2	
0x34	16-bit	2×	DDR two-lane bytewise	4 × f _S	See Figure 4	
0x24	16-bit	2×	DDR two-lane bitwise	4 × f _S	See Figure 4	
0x14	16-bit	2×	SDR two-lane bytewise	8 × f _S	See Figure 4	
0x04	16-bit	2×	SDR two-lane bitwise	8 × f _S	See Figure 4	
0x40	16-bit	1×	DDR one-lane wordwise	8 × f _S	See Figure 6	
0x32	12-bit	1×	DDR two-lane bytewise	3 × f _S	See Figure 3	
0x22	12-bit	1×	DDR two-lane bitwise	3 × f _S	See Figure 3	
0x12	12-bit	1×	SDR two-lane bytewise	6 × f _S	See Figure 3	
0x02	12-bit	1×	SDR two-lane bitwise	6 × f _S	See Figure 3	
0x36	12-bit	2×	DDR two-lane bytewise	3 × f _S	See Figure 5	
0x26	12-bit	2×	DDR two-lane bitwise	3 × f _S	See Figure 5	
0x16	12-bit	2×	SDR two-lane bytewise	6 × f _S	See Figure 5	

analog.com Rev. C | 35 of 38

MEMORY MAP

Table 20. SPI Register Options (Continued)

	Serialization Options Selected				
Register 0x21 Contents	Serial Output Number of Bits (SONB)	Frame Mode	Serial Data Mode	DCO Multiplier	Timing Diagram
0x06	12-bit	2×	SDR two-lane bitwise	6 × f _S	See Figure 5
0x42	12-bit	1×	DDR one-lane wordwise	6 × f _S	See Figure 7

analog.com Rev. C | 36 of 38

APPLICATIONS INFORMATION

DESIGN GUIDELINES

Before starting design and layout of the AD9645 as a system, it is recommended that the designer become familiar with these guidelines, which describe the special circuit connections and layout requirements that are needed for certain pins.

POWER AND GROUND GUIDELINES

When connecting power to the AD9645, it is recommended that two separate 1.8 V supplies be used. Use one supply for analog (AVDD); use a separate supply for the digital outputs (DRVDD). For both AVDD and DRVDD, several different decoupling capacitors should be used to cover both high and low frequencies. Place these capacitors close to the point of entry at the PCB level and close to the pins of the part, with minimal trace length.

If two supplies are used, AVDD must not power up before DRVDD. DRVDD must power up before, or simultaneously with, AVDD. If this sequence is violated, a soft reset via SPI Register 0x00 (Bits[7:0] = 0x3C), followed by a digital reset via SPI Register 0x08 (Bits[7:0] = 0x03, then Bits[7:0] = 0x00), restores the part to proper operation.

In non-SPI mode, the supply sequence is mandatory; in this case, violating the supply sequence is nonrecoverable.

A single PCB ground plane should be sufficient when using the AD9645. With proper decoupling and smart partitioning of the PCB analog, digital, and clock sections, optimum performance is easily achieved.

CLOCK STABILITY CONSIDERATIONS

When powered on, the AD9645 enters an initialization phase during which an internal state machine sets up the biases and the registers for proper operation. During the initialization process, the AD9645 needs a stable clock. If the ADC clock source is not present or not stable during ADC power-up, it disrupts the state machine and causes the ADC to start up in an unknown state. To correct this, reinvoke an initialization sequence after the ADC clock is stable by issuing a digital reset via Register 0x08. In the default configuration (internal V_{REF} , ac-coupled input) where V_{REF} and V_{CM} are supplied by the ADC itself, a stable clock during power-up is sufficient. In the case where V_{CM} is supplied by an external source, this, too, must be stable at power-up; otherwise, a subsequent digital reset via Register 0x08 is needed. The pseudo code sequence for a digital reset is as follows:

```
SPI_Write (0x08, 0x03);    # Digital Reset SPI_Write (0x08, 0x00);    # Normal Operation
```

EXPOSED PAD THERMAL HEAT SLUG RECOMMENDATIONS

It is required that the exposed pad on the underside of the ADC be connected to analog ground (AGND) to achieve the best electrical and thermal performance of the AD9645. An exposed continuous copper plane on the PCB should mate to the AD9645 exposed pad, Pin 0. The copper plane should have several vias to achieve the lowest possible resistive thermal path for heat dissipation to flow through the bottom of the PCB. These vias should be solder-filled or plugged.

To maximize the coverage and adhesion between the ADC and PCB, partition the continuous copper plane by overlaying a silk-screen on the PCB into several uniform sections. This provides several tie points between the ADC and PCB during the reflow process, whereas using one continuous plane with no partitions only guarantees one tie point. See Figure 71 for a PCB layout example. For detailed information on packaging and the PCB layout of chip scale packages, see the AN-772 Application Note, A Design and Manufacturing Guide for the Lead Frame Chip Scale Package (LFCSP), at www.analog.com.




Figure 71. Typical PCB Layout

VCM

The VCM pin should be decoupled to ground with a 0.1 μF capacitor

REFERENCE DECOUPLING

The VREF pin should be externally decoupled to ground with a low ESR, 1.0 μ F capacitor in parallel with a low ESR, 0.1 μ F ceramic capacitor.

SPI PORT

The SPI port should not be active during periods when the full dynamic performance of the converter is required. Because the SCLK, CSB, and SDIO signals are typically asynchronous to the ADC clock, noise from these signals can degrade converter performance. If the on-board SPI bus is used for other devices, it may be necessary to provide buffers between this bus and the AD9645 to prevent these signals from transitioning at the converter inputs during critical sampling periods.

analog.com Rev. C | 37 of 38

OUTLINE DIMENSIONS




Figure 72. 32-Lead Lead Frame Chip Scale Package [LFCSP] 5 mm × 5 mm Body and 0.75 mm Package Height (CP-32-12) Dimensions shown in millimeters

Updated: May 17, 2023

ORDERING GUIDE

Model ^{1, 2}	Temperature Range	Package Description	Packing Quantity	Package Option
AD9645BCPZ-125	-40°C to +85°C	32-Lead LFCSP (5mm x 5mm x 0.75mm w/ EP)		CP-32-12
AD9645BCPZ-80	-40°C to +85°C	32-Lead LFCSP (5mm x 5mm x 0.75mm w/ EP)		CP-32-12
AD9645BCPZRL7-125	-40°C to +85°C	32-Lead LFCSP (5mm x 5mm x 0.75mm w/ EP)	Reel, 1500	CP-32-12
AD9645BCPZRL7-80	-40°C to +85°C	32-Lead LFCSP (5mm x 5mm x 0.75mm w/ EP)	Reel, 1500	CP-32-12
AD9645WBCPZ-80	-40°C to +105°C	32-Lead LFCSP (5mm x 5mm x 0.75mm w/ EP)		CP-32-12
AD9645WBCPZRL7-80	-40°C to +105°C	32-Lead LFCSP (5mm x 5mm x 0.75mm w/ EP)	Reel, 1500	CP-32-12

Z = RoHS Compliant Part.

EVALUATION BOARDS

Model ¹	Description
AD9645-125EBZ	Evaluation Board

¹ Z = RoHS Compliant Part.

AUTOMOTIVE PRODUCTS

The AD9645W models are available with controlled manufacturing to support the quality and reliability of automotive applications. Note that these automotive models may have specifications that differ from the commercial models; therefore, designers should review the Specifications section of this data sheet carefully. Only the automotive grade product shown is available for use in automotive applications. Contact your local Analog Devices account representative for specific product ordering information and to obtain the specific Automotive Reliability reports for these models.



² W = Qualified for Automotive Applications.