

TOSHIBA CMOS Linear Integrated Circuit Silicon Monolithic

TCR3UF series


Ultra low quiescent current, Fast Load Transient 300 mA CMOS Low Dropout Regulator

1. Description

The TCR3UF series are CMOS process single output voltage regulators with an on/off control input, featuring ultra low quiescent bias current and low dropout voltage.

These voltage regulators are available in fixed output voltages between 0.8 V and 5.0 V and capable of driving up to 300 mA. They feature Overcurrent protection, thermal shutdown function and auto-discharge option.

The TCR3UF series is offered in general purpose package SMV (2.9 mm x 2.8 mm; t 1.1 mm (typ.)) and has a low dropout voltage of 206 mV (3.3 V output, IOUT = 300 mA). As small ceramic input and output capacitors 1 μF can be used with the TCR3UF series, these devices are ideal for portable applications that require high-density board assembly such as cellular phones, IoT equipment and wearable devices.



Weight: SMV (SOT-25)(SC-74A) : 16 mg (typ.)

2. Applications

Power IC developed for portable applications, IoT equipment and wearable devices

3. Features

- Low quiescent bias current (I_B = 0.34 μA (typ.) at IOUT = 0 mA, output voltage up to 1.5 V)
- High Ripple rejection ratio 70 dB at 0.8 V output
- Fast Load transient response -51/+36 mV at 0.8 V output, IOUT = 1 mA ⇔ 50 mA
- Low dropout voltage
 - VDO = 206 mV (typ.) at 3.3 V output, IOUT = 300 mA
- Wide range output voltage line up (VOUT = 0.8 to 5.0 V)
- High V_{OUT} accuracy ±1.0 % (1.8 V ≤ V_{OUT})
- Auto-discharge (TCR3UFxxA series)/ Non-discharge (TCR3UFxxB series) line up
- Overcurrent protection
- Thermal shutdown
- · Inrush current reduction
- Pull down connection between CONTROL and GND
- Ceramic capacitors can be used (CIN = 1 μ F, COUT = 1 μ F)
- General purpose package SMV(SOT-25) (SC-74A)

Start of commercial production 2019-09



4. Absolute Maximum Ratings (Ta = 25°C)

Characteristics	Symbol	Rating	Unit	
Input voltage	VIN	-0.3 to 6.0	V	
Control voltage	VcT	-0.3 to V _{IN} + 0.3 ≤ 6.0	V	
Output voltage	Vout	-0.3 to V _{IN} + 0.3 ≤ 6.0	V	
Davier discinstice		200 (Note1)	\/	
Power dissipation	P _D	580 (Note2)	mW	
Junction temperature	Tj	150	°C	
Storage temperature range	T _{stg}	−55 to 150	°C	

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note 1: Unit Rating

Note 2: Rating at mounting on a board

operating ranges.

(FR4 board: 25.4 mm × 25.4 mm × 1.6 mm)

5. Operating Ranges


Characteristics	Symbol		Rating		Unit
Input voltage	VIN		1.5 to 5.5	(Note 3)	V
Control voltage	Vст		0 to VIN		V
Output voltage	Vout	0.8 to 5.0			V
Output current	lout	DC 0 to 300 (Note 4)		mA	
Operating Temperature	Topr	-40 to 85			°C
Output Capacitance	Соит	≥ 1.0 µF			_
Input Capacitance	CIN	≥ 1.0 µF			_

Note 3: Please refer to Dropout voltage (Page 6) and use it within Absolute Maximum Ratings Junction temperature and Operating Temperature Ranges.

Note 4: Do not operate at or near the maximum ratings of operating ranges for extended periods of time. Exposure to such conditions may adversely impact product reliability and results in failures not covered by warranty.

6. Pin Assignment (top view)

SMV(SOT-25)(SC-74A)






7. List of Products Number, Output voltage and Marking

Product No.	Output voltage(V)	Auto- discharge	Marking	Product No.	Output voltage(V)	Auto- discharge	Marking
TCR3UF08A	0.8		0R8	TCR3UF08B	0.8		0T8
TCR3UF085A	0.85	-	0RA	TCR3UF085B	0.85		0TA
TCR3UF09A	0.9		0R9	TCR3UF09B	0.9		0T9
TCR3UF095A	0.95		0RB	TCR3UF095B	0.95		0TB
TCR3UF10A	1.0		1R0	TCR3UF10B	1.0		1T0
TCR3UF105A	1.05		1RC	TCR3UF105B	1.05		1TC
TCR3UF11A	1.1		1R1	TCR3UF11B	1.1		1T1
TCR3UF115A	1.15		1RE	TCR3UF115B	1.15		1TE
TCR3UF12A	1.2		1R2	TCR3UF12B	1.2		1T2
TCR3UF13A	1.3		1R3	TCR3UF13B	1.3		1T3
TCR3UF135A	1.35		1RF	TCR3UF135B	1.35		1TF
TCR3UF14A	1.4		1R4	TCR3UF14B	1.4		1T4
TCR3UF15A	1.5		1R5	TCR3UF15B	1.5		1T5
TCR3UF16A	1.6		1R6	TCR3UF16B	1.6		1T6
TCR3UF175A	1.75		1RG	TCR3UF175B	1.75		1TG
TCR3UF18A	1.8		1R8	TCR3UF18B	1.8		1T8
TCR3UF1825A	1.825		1RH	TCR3UF1825B	1.825		1TH
TCR3UF185A	1.85		1RJ	TCR3UF185B	1.85		1TJ
TCR3UF19A	1.9	Yes	1R9	TCR3UF19B	1.9	No	1T9
TCR3UF20A	2.0		2R0	TCR3UF20B	2.0		2T0
TCR3UF25A	2.5		2R5	TCR3UF25B	2.5		2T5
TCR3UF26A	2.6		2R6	TCR3UF26B	2.6		2T6
TCR3UF27A	2.7		2R7	TCR3UF27B	2.7		2T7
TCR3UF28A	2.8		2R8	TCR3UF28B	2.8		2T8
TCR3UF285A	2.85		2RK	TCR3UF285B	2.85		2TK
TCR3UF29A	2.9		2R9	TCR3UF29B	2.9		2T9
TCR3UF2925A	2.925		2RL	TCR3UF2925B	2.925		2TL
TCR3UF30A	3.0		3R0	TCR3UF30B	3.0		3T0
TCR3UF31A	3.1		3R1	TCR3UF31B	3.1		3T1
TCR3UF32A	3.2		3R2	TCR3UF32B	3.2		3T2
TCR3UF33A	3.3		3R3	TCR3UF33B	3.3		3T3
TCR3UF35A	3.5		3R5	TCR3UF35B	3.5		3T5
TCR3UF36A	3.6		3R6	TCR3UF36B	3.6		3T6
TCR3UF41A	4.1		4R1	TCR3UF41B	4.1		4T1
TCR3UF42A	4.2		4R2	TCR3UF42B	4.2		4T2
TCR3UF45A	4.5		4R5	TCR3UF45B	4.5		4T5
TCR3UF50A	5.0		5R0	TCR3UF50B	5.0		5T0


Top Marking (top view)



Example: TCR3UF33A (3.3 V output)



8. Block Diagram





9. Electrical Characteristics

(Unless otherwise specified,

 $V_{IN} = V_{OUT} + 1 V (V_{OUT} > 1.5 V), V_{IN} = 2.5 V (V_{OUT} \le 1.5 V), I_{OUT} = 50 \text{ mA}, C_{IN} = C_{OUT} = 1 \mu\text{F})$

Characteristics Symbol Test Condition		ondition	T _j = 25°C		T _j = -40 to 85°C (Note 10)		Unit		
					Тур.	Max	Min	Max	
Output valtage coourses	V	IOUT = 50 mA	Vout < 1.8 V	-18	_	+18	_	_	mV
Output voltage accuracy	Vout	(Note 5)	1.8 V ≤ V _{OUT}	-1.0	_	+1.0	_	_	%
Input voltage	VIN	I _{OUT} = 1 mA		1.5	_	5.5	1.5	5.5	V
Line regulation	Reg·line	IOUT = 1 mA	(Note 6)	_	1	15	_	_	mV
Load regulation	Reg·load	1 mA ≤ I _{OUT} ≤ 300 7)	mA (Note	_	21	30	_	_	mV
	IB(ON1)	IOUT = 0 mA, VOU	T ≤ 1.5 V (Note 8)	_	0.34	-	_	0.58	μΑ
Quiescent current	I _B (ON2)	I _{OUT} = 0 mA, 1.75 V ≤ V _{OUT} ≤ 5	V (Note 8)	_	0.38	_	_	0.68	μΑ
Chand by average	I _B (OFF1)	V _{CT} = 0 V, V _{IN} = 2	5 V	_	0.03	_	-	0.16	μA
Stand-by current	IB (OFF2)	VCT = 0 V, V _{IN} = 5.5 V		_	0.03	_	_	0.20	μA
Control pull down current	ICT	_		_	0.1		_	_	μΑ
Dropout voltage V _{DO}	V	I _{OUT} = 300 mA	V _{OUT} = 1.8 V	_	341	-	_	464	mV
	V DO		Vout = 3.3 V	_	206	_	_	287	mV
Output current limit	ICL	VOUT = VOUT(NOM) × 90% (Note 10)		_	545	_	400	_	mA
Output noise voltage	VNO	I _{OUT} = 10 mA, 10 Hz ≤ f ≤ 100 kHz, Ta = 25°C (Note 7)		_	41	_	_	_	μV _{rms}
Ripple rejection ratio	R.R.	IOUT = 10 mA, f = 1 kHz, VRipple = 200 mV _{p-p} , Ta = 25°C (Note 7)		_	70	_	_	_	dB
Load transient reanence	11/01/7	IOUT = 1 mA → 50	mA (Note 9)	_	-51	_	_	_	mV
Load transient response	∠Vout	IOUT = 50 mA → 1 mA (Note 9)		_	+36	_	_	_	mV
Temperature coefficient	T _{CVO}	-40°C ≤ T _{opr} ≤ 85°C		_	75	_	_	_	ppm/°C
Control voltage (ON)	VCT (ON)	_		1.0	_	5.5	1.0	5.5	V
Control voltage (OFF)	VCT (OFF)	_		0		0.4	0	0.4	V
Discharge on resistance	R _{SD}	V _{CT} = 0 V, V _{IN} = 5.5 V		_	7	-	5	20	Ω
Thermal shutdown temperature	T _{SD}	(Note 10) (Note 11)		_	158	_	_	_	°C
Thermal shutdown hysteresis	T _{SDH}	(Note 10) (Note 11)		_	28	_	_	_	°C

Note 5: stable state with fixed I_{OUT} condition Note 6: $V_{OUT} \le 1.5 \text{ V}$, 2.5 $V \le V_{IN} \le 5.5 \text{ V}$

 $1.75 \text{ V} \leq \text{VOUT} \leq 4.2 \text{ V}, \text{VOUT} + 1 \text{ V} \leq \text{VIN} \leq 5.5 \text{ V}$

VOUT = 4.5 V, VOUT = 5.0 V, not applicable

Note 7: Vout = 0.8V

Note 8: except Control pull down current (ICT)

Note 9: VOUT = 0.8 V, VIN = 3.3 V

Note 10: This parameter is warranted by design

Note 11: VOUT = 0.8 V, VIN = 2.5V



10. Dropout voltage

(Iout = 300 mA, C_{IN} = C_{OUT} = 1 μ F)


Output voltages	Symbol	Min	Typ. T _j = 25°C	Max (Note 12)	Unit
0.8 V ≤ V _{OUT} < 0.9 V		_	1020	1257	
0.9 V ≤ V _{OUT} < 1.0 V		_	933	1157	
1.0 V ≤ V _{OUT} < 1.1 V		_	848	1057	
1.1 V ≤ V _{OUT} < 1.2 V		_	760	957	
1.2 V ≤ V _{OUT} < 1.3 V		_	667	857	
1.3 V ≤ V _{OUT} < 1.5 V		_	580	757	
1.5 V ≤ V _{OUT} < 1.6 V	\/	_	462	617	
1.6 V ≤ V _{OUT} < 1.8 V	VDO	_	420	537	mV
1.8 V ≤ V _{OUT} < 2.0 V		_	341	464	
2.0 V ≤ V _{OUT} < 2.5 V		_	297	412	
2.5 V ≤ V _{OUT} < 3.0 V		_	226	342	
3.0 V ≤ V _{OUT} < 3.6 V		_	206	287	
3.6 V ≤ V _{OUT} < 4.5 V		_	184	245	
4.5 V ≤ V _{OUT} ≤ 5.0 V		_	159	224	

Note 12: $T_j = -40$ to 85 °C. This parameter is warranted by design



11. Application Note

11.1. Example of Application Circuit



CONTROL voltage	VOUT voltage
HIGH	ON
LOW	OFF
OPEN	OFF

The figure above shows the Example of configuration for using a Low dropout regulator. Insert a capacitor at Vout and VIN pins for stable input/output operation. (Ceramic capacitors can be used.)

11.2. Power Dissipation

Both unit and board-mounted power dissipation ratings for TCR3UF series are available in the Absolute Maximum Ratings table.

Power dissipation is measured on the board shown below.


[The Board Condition]

Board material: FR4 board

Board dimension: 25.4 mm \times 25.4 mm \times 1.6 mm

Copper area: 645 mm²

P_D - Ta (SMV)





Attention in Use

Output Capacitors

Ceramic capacitors can be used for these devices. However, because of the type of the capacitors, there might be unexpected thermal features. Please consider application condition for selecting capacitors. And Toshiba recommends the ESR of ceramic capacitor is under 10 Ω . For stable operation, we recommend over 1 μ F.

Mounting

The long distance between IC and input output capacitor might affect phase compensation by impedance in wire and inductor. For stable power supply, input output capacitor need to mount near IC as much as possible. Also V_{IN} and GND pattern need to be large and make the wire impedance small as possible.

Permissible Loss

Please have enough design patterns for expected maximum permissible loss. And under consideration of ambient temperature, input voltage, and output current etc., we recommend proper dissipation ratings for maximum permissible loss; in general maximum dissipation rating is 70 to 80 %.

Over current Protection and Thermal shutdown function


Over current protection and Thermal shutdown function are designed in these products, but these are not designed to constantly ensure the suppression of the device within operation limits. Depending on the condition during actual usage, it could affect the electrical characteristic specification and reliability. Also note that if output pins and GND pins are not completely shorted out, these products might break down.


When using these products, please read through and understand the concept of dissipation for absolute maximum ratings from the above mention or our 'Semiconductor Reliability Handbook'. Then use these products under absolute maximum ratings in any condition. Furthermore, Toshiba recommends inserting failsafe system into the design.





12. Representative Typical Characteristics


12.1. Output Voltage vs. Input Voltage





















12.2. Quiescent Current vs. Output Current





















12.3. Quiescent Current vs. Input Voltage



















12.4. Dropout Voltage vs. Output Current







12.5. Ripple Rejection Ratio vs. Frequency





12.6. Load Transient Response









12.7. ton Response






$V_{OUT} = 2.8V$




12.8. toff Response (Auto-discharge)

 $V_{OUT} = 2.8V$



 $V_{OUT} = 2.8V$




Note: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.




13. Package Information

SMV (SOT-25)(SC-74A)

Unit: mm





Weight: 16 mg (typ.)



RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE
 EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY
 CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT
 ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation,
 equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment,
 equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or
 explosions, safety devices, elevators and escalators, and devices related to power plant. IF YOU USE PRODUCT FOR UNINTENDED USE,
 TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our
 website.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR
 PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER,
 INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING
 WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2)
 DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR
 INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE,
 ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please
 use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including
 without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT
 OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.