Technical Information iTHERM CompactLine TM311

Compact thermometer, Pt100, 4-wire connection, class A

Optionally with integrated IO-Link and 4 to 20 mA transmitter, PC programmable



- Developed for universal use in hygienic and aseptic applications in the food & beverages and pharmaceutical industries, and for optimum standardization for machine and skid builders.
- Measuring range :-50 to +200 °C (-58 to +392 °F)
- Pressure range: up to 50 bar (725 psi)
- Protection class: IP69
- Output
 - Without electronics: Pt100 (4-wire connection)
 - With electronics: IO-Link, 4 to 20 mA, 1 x PNP switch output (depending on the type of connection)

Your benefits

Quick installation and easy commissioning:

- small, compact design, made entirely of stainless steel
- M12 connection with IP69 protection for easy electrical connection
- Pt100, 4-wire connection or self-detecting, universal output (IO-Link and 4 to 20 mA)
- Can also be ordered with preconfigured measuring range
- Recommended immersion lengths for optimum measurement at the highest level for standardization

Outstanding measurement properties thanks to innovative sensor technology:

- Extremely short response times
- Very accurate even with short immersion lengths
- Sensor-transmitter-matching increases measuring accuracy

Safe operation with certificates and approvals:

- Device safety according to EN 610101-1 and cCSAus
- Electromagnetic compatibility as per NAMUR NE21
- Diagnostics information can be selected according to NAMUR NE43
- Hygiene-compliant design with 3-A mark, EHEDG certification, ASME BPE conformity, FDA, EC 1935/2004, EN 2023/2006, TSE/ADI, GB4806-2016 and GB9685-2016
- Marine approval according to DNV GL



Table of contents

Function and system design	
Measuring principle	. 3
Measuring system	
Equipment architecture	4
Input	4
Measuring range	. 4
Output	5
Output signal	
Switching capacity	
Switch output	
Failure information	
Load	
Linearization/transmission behavior	
Damping	
Input current required	6
Maximum current consumption	
Switch-on delay	
Protocol-specific data	
Write protection for device parameters	
r	-
Power supply	7
Supply voltage	7
Power supply failure	7
Electrical connection	7
Overvoltage protection	
	. 0
	~
Performance characteristics	
Reference operating conditions	8
Reference operating conditions	8 8
Reference operating conditions	8 8 9
Reference operating conditions	8 8 9 10
Reference operating conditions	8 8 9 10 10
Reference operating conditions Maximum measured error Long-term drift Operating influences Device temperature Response time T ₆₃ and T ₉₀	8 8 9 10 10 10
Reference operating conditionsMaximum measured errorLong-term driftOperating influencesDevice temperatureResponse time T_{63} and T_{90} Electronics response time	8 9 10 10 10 10
Reference operating conditionsMaximum measured errorLong-term driftOperating influencesDevice temperatureResponse time T_{63} and T_{90} Electronics response timeSensor current	8 9 10 10 10 10 10
Reference operating conditionsMaximum measured errorLong-term driftOperating influencesDevice temperatureResponse time T_{63} and T_{90} Electronics response time	8 9 10 10 10 10
Reference operating conditions Maximum measured error Long-term drift Operating influences Device temperature Response time T ₆₃ and T ₉₀ Electronics response time Sensor current Calibration	8 9 10 10 10 10 10
Reference operating conditionsMaximum measured errorLong-term driftOperating influencesDevice temperatureResponse time T_{63} and T_{90} Electronics response timeSensor current	8 9 10 10 10 10 10
Reference operating conditions Maximum measured error Long-term drift Operating influences Device temperature Response time T ₆₃ and T ₉₀ Electronics response time Sensor current Calibration	8 8 9 10 10 10 10 10 10 10 10 11
Reference operating conditionsMaximum measured errorLong-term driftOperating influencesDevice temperatureResponse time T_{63} and T_{90} Electronics response timeSensor currentCalibration	8 8 9 10 10 10 10 10 10 10 10
Reference operating conditionsMaximum measured errorLong-term driftOperating influencesDevice temperatureResponse time T_{63} and T_{90} Electronics response timeSensor currentCalibrationOrientation	8 8 9 10 10 10 10 10 10 10 10 11
Reference operating conditions	8 8 9 10 10 10 10 10 10 10 10 11
Reference operating conditions	8 8 9 10 10 10 10 10 10 10 10 11 11
Reference operating conditions	8 8 9 10 10 10 10 10 10 10 10 10 10 10 10 10
Reference operating conditionsMaximum measured errorLong-term driftOperating influencesDevice temperatureResponse time T_{63} and T_{90} Electronics response timeSensor currentCalibrationOrientationInstallationOrientation instructionsEnvironmentAmbient temperature rangeStorage temperatureOperating altitudeClimate classDegree of protectionShock and vibration resistanceElectromagnetic compatibility (EMC)	8 8 9 10 10 10 10 10 10 10 10 10 10 11 11 11
Reference operating conditions	8 8 9 10 10 10 10 10 10 10 10 10 10 11 11 11
Reference operating conditions	8 8 9 10 10 10 10 10 10 10 10 10 10 10 10 10
Reference operating conditions Maximum measured error Long-term drift Operating influences Device temperature Response time T ₆₃ and T ₉₀ Electronics response time Sensor current Calibration Orientation Installation Orientation Installation instructions Storage temperature range Storage temperature Operating altitude Climate class Degree of protection Shock and vibration resistance Electromagnetic compatibility (EMC) Electrical safety	8 8 9 10 10 10 10 10 10 10 10 10 10 10 10 10
Reference operating conditions	8 8 9 10 10 10 10 10 10 10 10 10 10 10 10 10

Process pressure range	15 15
Mechanical construction	15 23 23 23 24 30
Human interface	31 31 32 32
Certificates and approvals . MTBF . Hygiene standard . Materials in contact with food/product (FCM) . CRN approval . CRN approval . Surface roughness . Material resistance .	32 32 32 32 32 32 32 33
Ordering information	33
Accessories	33 36 37 38
Documentation	39
Registered trademarks	39


Function and system design


Measuring principle	Resistance thermometer (RTD):			
	This insert uses a Pt100 according to IEC 60751 as the temperature sensor. The temperature sensor is a temperature-sensitive platinum resistor with a resistance of 100 Ω at 0 °C (32 °F) and a temperature coefficient α = 0.003851 °C ⁻¹ .			
	Thin film resistance sensors (TF):			
	A very thin, ultrapure platinum layer, approx. 1 μ m thick, is vaporized in a vacuum on a ceramic substrate and then structured photolithographically. The platinum conductor paths formed in this way create the measuring resistance. Additional covering and passivation layers are applied and reliably protect the thin platinum layer from contamination and oxidation, even at high temperatures. The primary advantages of thin film temperature sensors are their smaller sizes and better vibration resistance.			
Measuring system	The compact thermometer measures the process temperature with a Pt100 sensor element (class A, 4-wire). An optional built-in transmitter converts the Pt100 input signal. The version of the device with integrated electronics automatically detects the connection version (IO-Link or 4 to 20 mA).			
	A broad portfolio of optimized components for the temperature measuring point is available to ensure seamless integration of the measuring point: Power supply unit/barrier Display units Overvoltage protection IO-Link master IO-Link configuration tool			
	For more detailed information, see the brochure "System Products and Data Managers - Solutions for the loop (FA00016K/EN)".			
	PROFINET/ EtherNet/IP IO-Link SPS/PLC Master IO-Link ID-Link			

■ 1 M12 connection with IO-Link communication mode

TM311

A0039767





Equipment architecture

Design		Options	
	1: Electrical connection, output signal 2: Transmitter housing	 Your benefits: M12, 4-pin connector, reduced cost and effort, incorrect wiring is prevented Optimum protection, IP69 as standard Compact, integrated transmitter (IO-Link and 4 to 20 mA) 	
	3: Extension neck	Optionally available if process temperature is too high for the electronics	
	4: Process connection $\rightarrow \boxdot 24$	Over 50 different versions for industrial, hygienic and aseptic applications.	
	5: Thermowell	Versions with and without thermowell (insert in direct contact with process)Thermowell diameter 6 mm and optimized T-pieces and elbow pieces	
Ga G	6: Insert with: 6a: iTHERM TipSens 6b: Pt100 (TF), basic	 Your benefits: ITHERM TipSens - insert with shortest response times: Insert: Ø3 mm (¼ in) or Ø6 mm (¼ in) Fast, highly accurate measurements, delivering maximum process safety and control Quality and cost optimization Minimization of necessary immersion length: better product protection thanks to improved process flow Pt100 (TF), basic Excellent cost-performance ratio 	

Input

Measuring range	Pt100 (TF) basic	-50 to +150 °C (-58 to +302 °F)
	iTHERM TipSens	-50 to +200 °C (-58 to +392 °F)

	Output				
Output signal	Order code 020, option A				
	Sensor output	Pt100, 4-wire connection, class A			
	Order code 020, option B				
	Analog output 4 to 20 mA; variable measuring range				
	Digital output C/Q (IO-Link or switch output)				
	Order code 020, option C				
	Analog output	4 to 20 mA; measuring range 0 to 150 °C (32 to 302 °F)			
	Digital output	C/Q (IO-Link or switch output)			
Switching capacity	 1 × PNP switch output Switch state ON Ia ≤ 200 mA; switch state OFF Ia ≤ 10 µA Switch cycles > 10 000 000 Voltage drop PNP ≤ 2 V Overload protection Automatic load testing of switching current If a current of over 220 mA flows in the ON switch state, the device switches to a safe state Diagnostic message Overload at switch output Switch functions Hysteresis or window function NC contact or NO contact No pull-down resistor is integrated in the device for the switch output. 				
Switch output	Response time ≤ 100 ms				
Failure information		rated if the measuring information is missing or not valid. The device ic messages with the highest priority.			
		evice transmits all the failure information digitally.			
	In the 4 to 20 mA mode, th	e device transmits the failure information according to NAMUR NE43:			
	Switch output	The switch output switches to open in the fault state.			
	Underranging Overranging	Linear drop from 4.0 to 3.8 mA Linear increase from 20.0 to 20.5 mA			
	Failure e.g. sensor defective	$\leq 3.6 \text{ mA} \text{ (low) or } \geq 21 \text{ mA} \text{ (high) can be selected}$ The high alarm setting can be set between 21.5 mA and 23 mA, thus providing the flexibility needed to meet the requirements of various control systems.			
Load	R _{b max.} = (U _{b max.} - 10 V) / 0.02 output)	3 A (current			

Linearization/transmission behavior	Temperature - linear			
Damping	Configurable sensor input damping	0 to 120 s		
	Factory setting	0 s		
Input current required	 ≤ 3.5 mA for 4 to 20 mA ≤ 9 mA for IO-Link 			
Maximum current consumption	\leq 23 mA for 4 to 20 mA			
Switch-on delay	2 s			
Protocol-specific data	IO-Link information			
	IO-Link is a point-to-point connection for communication between the device and an IO-Link master. The IO-Link communication interface enables direct access to the process and diagnostic data. It also provides the option of configuring the device while in operation. <i>The device supports the following features:</i>			
	IO-Link specification	Version 1.1		
	IO-Link Smart Sensor Profile Edition	2nd Supported: Identification Diagnosis Digital Measuring Sensor (as per SSP type 3.1)		
	SIO mode	Yes		
	Speed	COM2; 38.4 kBaud		
	Minimum grale times	10		
	Minimum cycle time	10 ms		
	Process data width	4 byte		
	Process data width	4 byte Yes		

Device description

In order to integrate field devices into a digital communication system, the IO-Link system needs a description of the device parameters, such as output data, input data, data format, data volume and supported transfer rate.

This data is available in the device description (IODD ¹), which is provided to the IO-Link master via generic modules when the communication system is commissioned.

The IODD can be downloaded as follows: i

- Endress+Hauser: www.endress.com
 - IODDfinder: http://ioddfinder.io-link.com

Write protection for device Software write protection is implemented using system commands. parameters


IO Device Description 1)

Power supply

Supply voltage	Electronic version	Supply voltage					
	IO-Link/	U_{b} = 10 to 30 V_{DC} protected against reverse polarity					
	4 to 20 mA	IO-Link communication is quaranteed only if the supply voltage is at least 15 V.					
		If the supply voltage is < 15 V, the device displays a diagnostic message and					
	deactivates the switch output.						
	The device we	is the exercised with a time event in a type mitter never symply with Additional					
		ust be operated with a type-examined transmitter power supply unit. Additional rotection is required for marine applications.					
Power supply failure	 To meet electrical safety according to CAN/CSA-C22.2 No. 61010-1 or UL 61010-1, the demay only be powered by a power supply unit with a limited energy electric circuit in accorda with UL/EN/IEC 61010-1 chapter 9.4 or Class 2 according to UL 1310, "SELV or Class 2 circo." Behavior in the event of overvoltage (> 30 V) The device works continuously up to 35 V_{DC} without any damage. If the supply voltage is exact the specified characteristics are no longer guaranteed. Behavior in the event of undervoltage If the supply voltage falls below the minimum value ~ 7 V, the device switches off in a defined. 						
Electrical connection	According to t	as if not supplied with power).					
	smooth, corrosion-resistant and easy to clean.						
	M12 plug with 4 pins and "A" coding, in accordance with IEC 61076-2-101						
	 Do not overtighten the M12 plug, as this could damage the device. Maximum torque: 0.4 Nm (M12 knurl) 						
	In the version with electronics, the device function is defined by the pin assignment of the M12 connector. Communication is either IO-Link or 4 to 20 mA.						
	🗷 3 Pin assignme	A00403-					
	 Pin 1 - power supply 15 to 30 V_{DC} Pin 2 - not used Pin 3 - power supply 0 V_{DC} Pin 4 - C/Q (IO-Link or switch output) 						
	4 to 20 mA operating mode						
		A0040					

- Image: Pin assignment, device plug
- 1 Pin 1 power supply 10 to 30 V_{DC}
- 2 Pin 2 power supply 0 V_{DC}
- 3 Pin 3 not used
- 4 Pin 4 not used

Without electronics



Pin assignment of device plug: Pt100, 4-wire connection

Overvoltage protection

To protect against overvoltage in the power supply and signal/communication cables for the thermometer electronics, the manufacturer offers the HAW562 surge arrester for DIN rail mounting.

For more detailed information, see Technical Information HAW562 surge arrester I (TI01012K).

Performance characteristics

Reference operating conditions	Adjustment temperature (ice bath)	0 °C (32 °F) for sensor
	Ambient temperature range	25 °C ± 3 °C(77 °F ± 5 °F) for electronics
	Supply voltage	$24 V_{DC} \pm 10 \%$
	Relative humidity	< 95 %
Maximum measured error		60770 and the reference conditions specified above. The measured error Gaussian distribution). The data include non-linearities and repeatability.

Measured error (according to IEC 60751) in $^{\circ}C = 0.15 + 0.002 |T|$


|T| = Numerical value of the temperature in °C without regard to algebraic sign. •

Thermometer without electronics

Standard	Description	Measuring range	Measured error (±)	
			Maximum ¹⁾	Based on measured value ²⁾
IEC 60751	Pt100 Cl. A	–50 to +200 °C (–58 to +392 °F)	0.55 °C (0.99 °F)	ME = ± (0.15 °C (0.27 °F) + 0.002 * T)

Maximum measured error for the specified measuring range. 1)

2) Deviations from maximum measured error possible due to rounding.



Thermometer with electronics

Standard Description		Monguring rongo			
Stanuaru	Description	Measuring range	Digital ¹⁾		D/A ²⁾
		Maximum	Based on measured value		
IEC 60751	Pt100 Cl. A	–50 to +200 °C (–58 to +392 °F)	≤ 0.48 °C (0.86 °F)	ME = ± (0.215 °C (0.39 °F) + 0.134% * (MV - LRV))	0.05 % (≘ 8 μA)

Measured value transmitted via IO-Link. 1)

2) Percentages based on the configured span of the analog output signal.

Standard	Description	Monouving vongo	Measured error (±)		
Stanuaru	Description	Measuring range	Digital ¹⁾		D/A ²⁾
		Maximum	Based on measured value		
IEC 60751	Pt100 Cl. A	–50 to +200 °C (–58 to +392 °F)	≤ 0.14 °C (025 °F)	ME = ± (0.127 °C (0.23 °F) + 0.0074% * (MV - LRV))	0.05 % (≙ 8 μA)

Thermometer with electronics and sensor-transmitter-matching / increased accuracy

1) Measured value transmitted via IO-Link.

2) Percentages based on the configured span of the analog output signal.

MV = measured value

LRV = lower range value of the sensor in question

Total measured error of transmitter at current output = $\sqrt{(Measured error digital^2 + Measured error D/A^2)}$

Sample calculation with Pt100, measuring range 0 to +150 $^{\circ}$ C (+32 to +302 $^{\circ}$ F), ambient temperature+25 $^{\circ}$ C (+77 $^{\circ}$ F), supply voltage24 V and sensor-transmitter matching:

Measured error digital = 0.127 °C (0.229 °F) + 0.0074 % x [150 °C (302 °F) - (-50 °C (-58 °F))]:	0.14 °C (0.25 °F)
Measured error D/A = 0.05 % x 150 °C (302 °F)	0.08 °C (0.14 °F)
Measured error digital value (IO-Link):	0.14 °C (0.25 °F)
Measured error analog value (current output): $\sqrt{(Measured error digital^2 + Measured error D/A^2)}$	0.16 °C (0.29 °F)

Sample calculation with Pt100, measuring range 0 to +150 $^{\circ}$ C (+32 to +302 $^{\circ}$ F), ambient temperature +35 $^{\circ}$ C (+95 $^{\circ}$ F), supply voltage 30 V:

Measured error digital = 0.215 °C (0.387 °F) + 0.134% x [150 °C (302 °F) - (-50 °C (-58 °F))]:	0.48 °C (0.86 °F)
Measured error D/A = 0.05 % x 150 °C (302 °F)	0.08 °C (0.14 °F)
Influence of ambient temperature (digital) = (35 - 25) x (0.004 % x 200 °C (360 °F)), at least 0.008 °C (0.014 °F)	0.08 °C (0.14 °F)
Influence of ambient temperature (D/A) = (35 - 25) x (0.003 % x 150 $^{\circ}$ C (302 $^{\circ}$ F))	0.05 °C (0.09 °F)
Influence of supply voltage (digital) = (30 - 24) x (0.004 % x 200 °C (360 °F)), at least 0.008 °C (0.014 °F)	0.05 °C (0.09 °F)
Influence of supply voltage (D/A) = (30 - 24) x (0.003 % x 150 °C (302 °F))	0.03 °C (0.05 °F)
Measured error digital value (IO-Link): $\sqrt{(\text{Measured error digital}^2 + \text{Influence of ambient temperature (digital)}^2 + \text{Influence of supply voltage (digital)}^2}$	0.49 °C (0.88 °F)
Measured error analog value (current output): $\sqrt{(Measured error digital^2 + Measured error D/A^2 + Influence of ambient temperature (digital)^2 + Influence of ambient temperature (D/A)^2 + Influence of supply voltage (digital)^2 + Influence of supply voltage (D/A)^2}$	0.50 °C (0.90 °F)

Long-term drift

	1 month	3 months	6 months	1 year	3 years	5 years
Digital output IO-Link	±9 mK	± 15 mK	± 19 mK	±23 mK	±28 mK	±31 mK
Current output Measuring range –50 to +200 °C (–58 to +360 °F)	±2.5 μΑ	±4.3 μA	±5.4 μΑ	±6.4 μΑ	± 8.0 µA	±8.8 µA

 $D/A^{2)}$

Supply voltage Influence (+-) per 1 V change

Based on measured value 4)

Digital 1)

Maximum³⁾

IEC 60751	Pt100 Cl. A	0.014 °C (0.025 °F)	0.004 % * (MV - LRV), min. 0.008 °C (0.0144 °F)	0.003 % (≘0.48 µA)	0.014 °C (0.025 °F)	0.004 % * (MV - LRV), min. 0.008 °C (0.0144 °F)	0.003 % (≘0.48 μA)
2) Percei 3) Maxir	ntages based o num measure	l error for the speci ximum measured e	an of the analog output s fied measuring range. rror possible due to round	-			
			Measured value Lower range value of 1	relevant sensor			
			5		nt output = √(M	easured error digital ² +	Measured erro
Device tem	perature	The di	splayed device temper	ature has a max	timum measured	l error of ±8 K.	
Response t	time T ₆₃ and	10 K. I	n water at 0.4 m/s (1. Response times measu nse time without heat t	red for the vers		temperature changes in tronics.	increments of
			Design		Sensor	t63	t ₉₀
		6 mm tip	direct contact, straight	Pt100 (TF) basic		5 s	< 20 s
		6 mm tip	direct contact, straight	iTHERM TipSens		1 s	1.5 s
			thermowell, straight tip 20 mm)	iTHERM TipSens		1 s	3 s
		Respor	use time with heat tran	asfer paste ¹⁾			
			Design		Sensor	t63	t ₉₀
			thermowell, straight tip 20 mm)	iTHERM TipSer	IS	1 s	2.5 s
		1) I	Between the insert and th	ne thermowell			
Electronics	s response ti	V				in mind that the respon	se times of the
Sensor cur	rent	≤ 1 mA	A				
Calibratior	n	Calibra more r to dete variab • Calil	precise calibration stan ermine the deviation of le. Two different meth	ng the measure idard using a de f the DUT's mea ods are used for cemperatures, e	fined and repro- sured values fro thermometers: .g. at the freezin	g point of water at 0 °C	ethod. The aim

Operating influences The measured error data correspond to $\pm 2 \sigma \sigma$ (Gaussian distribution).

Digital 1)

Maximum³⁾

Designation

Standard

Ambient temperature Influence (+-) per 1 °C (1.8 °F) change

Based on measured value 4)

D/A²⁾

The thermometer to be calibrated must display the fixed point temperature or the temperature of the reference thermometer as accurately as possible. Temperature-controlled calibration baths with very homogeneous thermal values, or special calibration furnaces into which the DUT and the reference thermometer, where necessary, can project to a sufficient degree, are typically used for thermometer calibrations.

Sensor-transmitter-matching

The resistance/temperature curve of platinum resistance thermometers is standardized but in practice it is rarely possible to keep to the values precisely over the entire operating temperature range. For this reason, platinum resistance sensors are divided into tolerance classes, such as class A, AA or B as per IEC 60751. These tolerance classes describe the maximum permissible deviation of the specific sensor characteristic curve from the standard curve, i.e. the maximum temperature-dependent characteristic error that is permitted. The conversion of measured sensor resistance values at temperatures in temperature transmitters or other meter electronics is often susceptible to considerable errors as the conversion is generally based on the standard characteristic curve.

When temperature transmitters are used, this conversion error can be reduced significantly by sensor-transmitter-matching:

- Calibration at least at three temperatures and determination of the actual temperature sensor characteristic curve
- Adjustment of the sensor-specific polynomial function using appropriate Calendar-van-Dusen (CvD) coefficients
- Configuration of the temperature transmitter with the sensor-specific CvD coefficients for resistance/temperature conversion, and
- another calibration of the reconfigured temperature transmitter with the connected resistance thermometer


The manufacturer offers this sensor-transmitter-matching as a separate service. Furthermore, the sensor-specific polynomial coefficients of platinum resistance thermometers are indicated on every calibration protocol where possible, e.g. at least three calibration points.

For the device, the manufacturer offers standard calibrations at a reference temperature of -50 to +200 °C (-58 to +392 °F) based on the ITS90 (International Temperature Scale). Calibrations in other temperature ranges are available from your local sales center on request. Calibrations are traceable to national and international standards. The calibration certificate is referenced to the serial number of the device.

Installation

Orientation	No restrictions. However, self-draining in the process must be guaranteed. If there is an opening to detect leaks at the process connection, this opening must be at the lowest possible point.
Installation instructions	The immersion length of the compact thermometer can considerably influence the accuracy. If the immersion length is too short, measurement errors can occur as a result of heat conduction via the process connection and the vessel wall. Therefore, if installing in a pipe, the immersion length should ideally correspond to half of the pipe diameter.

Installation possibilities: pipes, tanks or other plant components.



6 Installation examples


- 1, 2 Perpendicular to flow direction, installed at a minimum angle of 3°, to ensure self-draining
- 3 On elbows
- 4 Inclined installation in pipes with a small nominal diameter
- U Immersion length

The requirements of the EHEDG and the 3-A Sanitary Standard must be adhered to.

Installation instruction EHEDG/cleanability: $Lt \leq (Dt-dt)$

Installation instruction $3-A/cleanability: Lt \le 2(Dt-dt)$

Pay attention to the exact position of the sensor element in the thermometer tip.



- 1 StrongSens or TrustSens at 5 to 7 mm (0.2 to 0.28 in)
- 2 QuickSens at 0.5 to 1.5 mm (0.02 to 0.06 in)
- 3 Thermocouple (not grounded) at 3 to 5 mm (0.12 to 0.2 in)
- 4 Wire wound sensor at 5 to 20 mm (0.2 to 0.79 in)
- 5 Standard thin-film sensor at 5 to 10 mm (0.2 to 0.39 in)


To keep the influence of heat dissipation to a minimum and to achieve the best possible measurement results, 20 to 25 mm (0.79 to 0.98 in) should be in contact with the medium in addition to the actual sensor element.

This results in the following recommended minimum immersion lengths

- TrustSens or StrongSens 30 mm (1.18 in)
- QuickSens 25 mm (0.98 in)
- Wire wound sensor 45 mm (1.77 in)
- Standard thin-film sensor 35 mm (1.38 in)

It is particularly important to take this into consideration for T-pieces, as the immersion length is very short on account of their design, and the measured error is higher as a result. It is therefore recommended to use elbow pieces with QuickSens sensors.

In the case of pipes with a small nominal diameter, it is advisable for the tip of the thermometer to project well into the process so that it extends past the pipe axis. Installation at an angle (4) could be another solution. When determining the immersion or insertion length, all the parameters of the thermometer and of the medium to be measured must be taken into account (e.g. Flow velocity, process pressure).



- ☑ 7 Detailed installation instructions for hygiene-compliant installation
- A Milk pipe connection according to DIN 11851, only in conjunction with EHEDG-certified, self-centering sealing ring
- 1 Sensor with milk pipe connection
- 2 Groove slip-on nut
- 3 Counterpart connection
- 4 Centering ring
- 5 RO.4
- 6 R0.4 7 Sealina i
- 7 Sealing ring
 B Varivent[®] process connection for VARI
- B Varivent[®] process connection for VARINLINE[®] housing
- 8 Sensor with Varivent connection9 Counterpart connection
- 10 O-ring
- *C Clamp according to ISO 2852*
- 11 Molded seal
- 12 Counterpart connection
- D Process connection Liquiphant-M G1", horizontal installation
- 13 Weld-in adapter
- 14 Vessel wall
- 15 O-ring
- 16 Thrust collar

NOTICE

The following actions must be taken if a sealing ring (O-ring) or seal fails:

- ▶ The thermometer must be removed.
- ► The thread and the O-ring joint/sealing surface must be cleaned.
- The sealing ring or seal must be replaced.
- ► CIP must be performed after installation.

In the case of weld-in connections, exercise the necessary degree of care when performing the welding work on the process side:

- 1. Use suitable welding material.
- **2.** Flush-weld or weld with welding radius \geq 3.2 mm (0.13 in).
- 3. Avoid crevices, folds or gaps.
- 4. Ensure the surface is honed and mechanically polished, $Ra \le 0.76 \mu m$ (30 μin).

Pay attention to the following when installing the thermometer to ensure that the cleanability is not affected:

- 1. The installed sensor is suitable for CIP (cleaning in place). Cleaning is performed together with the pipe or tank. In the case of internal tank fixtures using process connection nozzles, it is important to ensure that the cleaning assembly sprays this area directly so that it is cleaned properly.
- 2. The Varivent[®] connections enable flush-mounted installation.

Environment

Ambient temperature range	T _a	-40 to +85 °C (-40 to +185 °F)			
Storage temperature	T _s	-40 to +85 °C (-40 to +185 °F)			
Operating altitude	Up to 2 000 m (6 600 ft) a	bove sea level			
Climate class	In accordance with IEC/EN	160654-1, climate class Dx, class 4K4H			
Degree of protection	As per IEC/EN 60529 IP69	9			
	Depends on the degree	ee of protection of the connection cable $\rightarrow \square$ 36			
Shock and vibration resistance	The thermometer meets the resistance of 3 g in the 10	he requirements of IEC 60751, which specifies shock and vibration to 500 Hz range.			
Electromagnetic compatibility (EMC)	EMC in accordance with all the relevant requirements of the IEC/EN 61326 series and NAMUR Recommendation EMC (NE21). For details, refer to the Declaration of Conformity.				
	 Interference immunity a 	ror under EMC tests: < 1 % of the span according to IEC/EN 61326 series, requirements for industrial fields ccording to IEC/EN 61326 series, Class B equipment			
	IO-Link				
	Only the requirements of IEC/EN 61131-9 are met in I/O-Link mode.				
	The connection between the IO-Link master and thermometer is via an unshielded 3-wire cable, maximum 20 m (65.6 ft) in length.				
	4 to 20 mA				
	Electromagnetic compatib series and NAMUR Recom	ility in accordance with all the relevant requirements of the IEC/EN 61326 mendation EMC (NE21).			
	For more information, see the Declaration of Conformity.				
	1. With a connection cable length of 30 m (98.4 ft): always use a shielded cable.				
	2. The use of shielded connection cables is generally recommended.				
Electrical safety	 Protection class III Overvoltage category II Pollution level 2 				

	Process			
Process temperature range	The thermometer electronics must be protected against temperatures over 85 °C (185 °F) by an extension neck of the appropriate length.			
	Device version without el	lectronics (order code 020, option A)		
	Pt100 TF, basic, without extension neck	-50 to +150 °C (-58 to +302 °F)		
	Pt100 TF, basic, with extension neck	-50 to +150 °C (-58 to +302 °F)		
	iTHERM TipSens, without extension neck	-50 to +200 °C (-58 to +392 °F)		
	iTHERM TipSens, with extension neck	–50 to +200 °C (–58 to +392 °F)		
	Device version with elect	ronics (order code 020, option B, C)		
	Pt100 TF, basic, without extension neck	-50 to +150 °C (-58 to +302 °F)		
	Pt100 TF, basic, with extension neck	-50 to +150 °C (-58 to +302 °F)		
	iTHERM TipSens, without extension neck	-50 to +150 °C (-58 to +302 °F)		
	iTHERM TipSens, with extension neck	-50 to +200 °C (-58 to +392 °F)		
Thermal shock	Thermal shock resistance in CIP/SIP process with a temperature increase from +5 to +130 $^{\circ}$ C (+41 to +266 $^{\circ}$ F) within 2 seconds.			
Process pressure range	The maximum possible process pressure depends on various influence process connection and process temperature. Maximum possible pro process connections. $\rightarrow \cong 24$			
	It is possible to verify the mechanical loading capacity as a function of the installation and process conditions using the online TW Sizing Module for thermowells in the Endress+Hauser Applicator software . → 🗎 33			
Medium - state of aggregation	Gaseous or liquid (also wit	h high viscosity, e.g. yogurt).		
	Mechanical cor	nstruction		
Design, dimensions	All dimensions in mm (in)	. The design of the thermometer depends on the thermowell version used:		

- Thermometer without thermowell
- Thermowell diameter 6 mm (¹/₄ in)
- T-piece and corner-piece thermowell version as per DIN 11865/ASME BPE 2012 for welding in


Various dimensions, such as the immersion length U for example, are variable values and are therefore indicated as items in the following dimensional drawings.

Variable dimensions:

Item	Description
В	Thermowell bottom thickness
E	Extension neck length, optional

Item	Description
Т	Length of thermowell lagging, pre-defined, depending on the thermowell version
U	Variable immersion length, depending on the configuration

Without thermowell




1 Thermometer with spring-loaded cap-nut, G3/8" thread 3 mm for existing thermowell

- 2 Thermometer with spring-loaded NPT¹/₂" male thread 3 mm for existing thermowell
- 3 Thermometer without process connection for compression fitting, with extension neck
- 4 Thermometer with G¹/₂" male thread
- 5 Thermometer with G¹/₄" male thread
- 6 Thermometer without electronics


When using an extension neck, the overall length of the device always increases by the length in question, E = 50 mm (1.97 in), regardless of the process connection.

Pay attention to the following equations when calculating the immersion length U for an existing thermowell:


Version 1 (G3/8" cap-nut)	$U = U_{(thermowell)} + T_{(thermowell)} + 3 mm - B_{(thermowell)}$
Version 2 (NPT½" male thread)	$ \begin{array}{l} U = U_{(thermowell)} + T_{(thermowell)} - 5 \ mm \ _{(-8 \ mm \ screw-in \ depth \ + \ 3mm \ spring \ travel)} - \\ B_{(thermowell)} \end{array} $



- 1 Thermometer with M14 male thread
- Thermometer with M18 male thread
- 2 3 Thermometer with NPT¹/2" male thread
- 4 Thermometer with NPT¹/₄" male thread
- 5 Thermometer with Microclamp, DN18 (0.75")
- 6 Thermometer with Tri-Clamp, DN18 (0.75")




- Thermometer with Clamp ISO2852 for DN12 to 21.3, DN25 to 38, DN40 to 51 1
- 2 3 Thermometer with milk pipe connection DIN11851 for DN25/DN32/DN40/DN50
- Thermometer with metal sealing system G¹/₂"
- 4 Thermometer with G¾" male thread ISO228 for FTL31/33/20/50 Liquiphant adapter
- 5 Thermometer with D45 process adapter




- 1 Thermometer with APV in-line, DN50
- 2 Thermometer with Varivent type B, D 31 mm
- 3 Thermometer with Varivent type F, D 50 mm and Varivent type N, D 68 mm
- 4 Thermometer with SMS 1147, DN25/DN38/DN51

With compression fitting



- $1 \qquad Thermometer \ with \ compression \ fitting \ TK40 \ spherical, \ PEEK/316L, \ sleeve, \ \varnothing \ 25 \ mm, \ for \ welding \ in$
- $2 \qquad Thermometer with compression fitting TK40 \ cylindrical, Elastosil sleeve, \varnothing \ 25 \ mm, for welding \ in$
- 3 Thermometer with compression fitting G¹/₂" external thread, TK40-BADA3C, 316L

With thermowell diameter 6 mm $(\frac{1}{4} in)$



Thermometer with weld-in adapter cylindrical, D 12 \times 40 mm40mm Thermometer with weld-in adapter cylindrical, D 30 x 40 mm 1


2

Thermometer with weld-in adapter spherical-cylindrical, D 30 x 40 mm Thermometer with weld-in adapter spherical, D 25 mm 3


4

5 Thermometer with milk pipe connection DIN11851, DN25/DN32/DN40

6 Thermometer with Microclamp, DN18 (0.75")




- 1 Thermometer with Tri-Clamp version DN18
- 2
- Thermometer with Clamp version DN12 to 21.3 Thermometer with Clamp version DN25 to 38/DN40 to 51 3
- 4 Thermometer with metal sealing system version, $M12 \times 1.5$
- Thermometer with metal sealing system version, G¹/₂"
- 5 6 Thermometer without process connection



- 1 Thermometer with compression fitting TK40 cylindrical, Elastosil sleeve, Ø30 mm, for welding in
- 2 Thermometer with compression fitting TK40 spherical, PEEK/316L sleeve, Ø25 mm, for welding in

Thermowell version as T-piece or elbow piece



- 1 Thermometer with tee thermowell
- 2 Thermometer with elbow thermowell
- Pipe sizes as per DIN 11865 series A (DIN), B (ISO) and C (ASME BPE)
- 3-A mark for nominal diameters \geq DN25
- IP69 protection
- Material 1.4435+316L, delta ferrite content < 0.5%
- Temperature range -60 to +200 °C (-76 to +392 °F)
- Pressure range PN25 as per DIN11865



Due to the short immersion length U in the case of small pipe diameters, the use of iTHERM TipSens inserts is recommended.

Process connection and size	Direct contact,6 mm (¼ in)	Thermowell,6 mm (¼ in)					
Without process connection (for installation with compression fitting)	Ø	V					
Process adapter D45		-					
Compression fitting							
Thread G ¹ /2"	V						
Cylindrical Ø30 mm	V						
Spherical Ø25 mm		✓					
Thread		I					
G½"	V	-					
G¼"	V	-					
M14x1.5	V	-					
M18x1.5	V	-					
NPT ¹ /2"		-					
Weld-in adapter	1	I					
Cylindrical Ø30 x 40 mm	-						
Cylindrical Ø12 x 40 mm	-						
Spherical-cylindrical Ø30 x 40 mm	-						
Spherical Ø25 mm (0.98 in)	-						
Clamps according to ISO 2852		I					
Microclamp/Tri-clamp DN18 (0.75 in)							
DN12 - 21.3							
DN25 -38 (1 - 1.5 in)							
DN40 - 51 (2 in)							
Milk pipe connection according to DIN 11851							
DN25							
DN32							
DN40							
DN50		-					
Metal sealing system							
M12x1	-						
G ¹ /2"							
Thread according to ISO 228 for Liquiphant weld	-in adapter						
G¾" for FTL20, FTL31, FTL33		-					
G¾" for FTL50		-					
G1" for FTL50		-					
APV Inline							
DN50		-					
Varivent®		I					
Type B, Ø31 mm		-					
Type F, Ø50 mm		-					
Type N, Ø68 mm		-					
SMS 1147		1					

Possible combinations of the thermowell versions with the available process connections

Process connection and size	Direct contact,6 mm ($\frac{1}{4}$ in)	Thermowell,6 mm (¼ in)
DN25	\checkmark	-
DN38	V	-
DN51	V	-

Weight

0.2 to 2.5 kg (0.44 to 5.5 lbs) for standard versions

Material

The temperatures for continuous operation specified in the following table are only intended as reference values for use of the various materials in air and without any significant compressive load. The maximum operating temperatures can be reduced considerably in cases where abnormal conditions such as high mechanical load occur or in aggressive media.

Description	Short form	Recommended max. temperature for continuous use in air	Properties			
AISI 316L (corresponds to 1.4404 or 1.4435)	X2CrNiMo17-13-2, X2CrNiMo18-14-3	650 °C (1202 °F) ¹⁾	 Austenitic, stainless steel High corrosion resistance in general Particularly high corrosion resistance in chlorine-based and acidic, non-oxidizing atmospheres through the addition of molybdenum (e.g. phosphoric and sulfuric acids, acetic and tartaric acids with a low concentration) Increased resistance to intergranular corrosion and pitting 			
1.4435+316L, delta ferrite < 1% or < 0.5%	addition, the delta ferrite con	alytical limits, the specifications of both materials (1.4435 and 316L) are met simultaneously. In a ferrite content of the parts in contact with the process is limited to <1% or <0.5%. ns (in accordance with Basel Standard II)				

1) Can be used to a limited extent up to 800 °C (1472 °F) for low compressive loads and in non-corrosive media. More information is available from the sales organization.

Surface roughness	Values for wetted surfaces:	
	Standard surface, mechanically polished ¹⁾	$R_a \le 0.76 \ \mu m (30 \ \mu in)$
	Mechanically polished ¹⁾ , buffed ²⁾	$R_a \le 0.38 \ \mu m \ (15 \ \mu in)$
	Mechanically polished ¹⁾ , buffed and electropolished	$R_a \le 0.38 \ \mu m \ (15 \ \mu in) + electropolished$

1) Or equivalent treatment that guarantees R_a max

2) Not compliant with ASME BPE

Process connections

Compression fitting

Type TK40	Vorsion	Version		Technical properties	
Type IK40	VEISIOII	Ødi	L	Across flats	reclinical properties
A0039490 1 Nut 2 Clamping sleeve 3 Process connection	G ½" , ferrule material 316L	6 mm (0.24 in)	Approx. 47 mm (1.85 in)	G½": 27 mm (1.06 in)	 P_{max.} = 40 bar (104 psi) at T = +200 °C (+392 °F) for 316L P_{max.} = 25 bar (77 psi) at T = +400 °C (+752 °F) for 316L Tightening torque = 40 Nm

Type TK40 for weld-in	Version		Dimensions		Technical properties ¹⁾
Type 1K40 for weid-in	Spherical or cylindrical	Ødi	ΦD	h	Technical properties
	d Spherical Material of sealing taper PEEK or 316L Thread G¼"	6.3 mm (0.25 in) ²⁾	25 mm (0.98 in)	33 mm (1.3 in)	 P_{max.} = 10 bar (145 psi) T_{max.} for PEEK sealing taper = +150 °C (+302 °F), tightening torque = 10 Nm P_{max.} = 50 bar (725 psi) T_{max.} for 316L sealing taper = +200 °C (+392 °F), tightening torque = 25 Nm The TK40 PEEK sealing taper is EHEDG tested and 3- A marked
	Cylindrical Sealing taper material Elastosil® Thread G½"	6.2 mm (0.24 in) ²⁾	30 mm (1.18 in)	57 mm (2.24 in)	 P_{max.} = 10 bar (145 psi) T_{max.} for Elastosil[®] sealing taper = +150 °C (+302 °F), tightening torque = 5 Nm The TK40 Elastosil sealing taper is EHEDG tested and 3-A marked

All the pressure specifications apply for cyclic temperature load For insert or thermowell diameter Ød = 6 mm (0.236 in).1)

2)

Releasable process connection

	Dimensions				
Туре	Version G	L1 thread length	A	Across flats	Technical properties
Thread	G¼" ISO228	16 mm	25 5 mm (1 in)	2.2	- D - 25 har (262 noi) at
	G½" ISO228	(0.63 in)	25.5 mm (1 in)	32	 P_{max.} = 25 bar (362 psi) at max. 150 °C (302 °F) P_{max.} = 40 bar (580 psi) at
00040000	M14x1.5	18.6 mm (0.73 in)	29.5 mm (1.16 in)	41	max. 100 ℃ (212 ℉)

			Dimensions		
Туре	Version G	L1 thread length	А	Across flats	Technical properties
	M18x1.5				
	½" NPT ANSI				

Time	Version	D	Dimensions	- Technical properties
Туре	Ød 1)	ΦD	Фа	Technical properties
Clamp according to ISO 2852	DN8-18 (0.5"-0.75") ³⁾		-	• P _{max.} = 16 bar (232 psi), depends on clamp ring and
	Tri-clamp DN8-18 (0.5"-0.75") ³⁾	25 mm (0.98 in)	-	suitable seal • 3-A marked
	DN12-21.3	34 mm (1.34 in)	16 to 25.3 mm (0.63 to 0.99 in)	• P _{max.} = 16 bar (232 psi), depends on clamp ring and
	DN25-38 (1"-1.5")	50.5 mm (1.99 in)	29 to 42.4 mm (1.14 to 1.67 in)	 suitable seal 3-A marked and EHEDG certified (in connection with
	DN40-51 (2")	64 mm (2.52 in)	44.8 to 55.8 mm (1.76 to 2.2 in)	Combifit seal) ASME BPE compliance
ØD ØD Ød Ød Form A				
Form B				
A Different seal geometries for Microclamp and Tri-clamp				

1)

2) 3)

Pipes in accordance with ISO 2037 and BS 4825 Part 1 Microclamp (not in ISO 2852); no standard pipes DN8 (0.5") only possible with thermowell diameter = 6 mm (¼ in)

	Тур	е				Technical properties
						 3-A marked and EHEDG certified (only with EHEDG certified and self-centering sealing ring) ASME BPE compliance
Version ¹⁾			Dimensions			- P _{max.}
	ΦD	А	В	Øi	Фа	* max.
DN25	44 mm (1.73 in)	30 mm (1.18 in)	10 mm (0.39 in)	26 mm (1.02 in)	29 mm (1.14 in)	40 bar (580 psi)
DN32	50 mm (1.97 in)	36 mm (1.42 in)	10 mm (0.39 in)	32 mm (1.26 in)	35 mm (1.38 in)	40 bar (580 psi)
DN40	56 mm (2.2 in)	42 mm (1.65 in)	10 mm (0.39 in)	38 mm (1.5 in)	41 mm (1.61 in)	40 bar (580 psi)
DN50	68 mm (2.68 in)	54 mm (2.13 in)	11 mm (0.43 in)	50 mm (1.97 in)	53 mm (2.1 in)	25 bar (363 psi)

1) Pipes in accordance with DIN 11850

Ту	Version	Technical properties			
Metal seal	Metal sealing system				
M12x1.5	G ¹ /2"				
$\begin{array}{c} 14 \\ (0.55) \\ \hline \\ $	$\begin{array}{c} 14 \\ 8 \\ 0.31 \\ \hline \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ $	Thermowell diameter 6 mm (¼ in)	P _{max.} = 16 bar (232 psi) Maximum torque = 10 Nm (7.38 lbf ft)		

		Dimensions			
Туре	Version G	L1 thread length	A	1 (SW/AF)	Technical properties
Thread according to ISO 228 (for Liquiphant weld-in adapter)	G¾" for FTL20/31/33 adapter	16 mm	25.5 mm (1 in)	32	 P_{max} = 25 bar (362 psi) at max. 150 °C (302 °F)
	G¾" for FTL50 adapter	(0.63 in)			 P_{max.} = 40 bar (580 psi) at max. 100 °C (212 °F) 3-A marked and EHEDG tested ASME BPE compliance
U A0009572	G1" for FTL50 adapter	18.6 mm (0.73 in)	29.5 mm (1.16 in)	41	

Туре	Version	Technical properties
Process adapter		
0070 (1.97) 045 (1.77) 007 00 007 00 007 007	D45	

For welding in

Туре	Version Dimensions		Technical properties
Weld-in adapter	1: Cylindrical	¢d x h = 12 mm (0.47 in) x 40 mm (1.57 in), T = 55 mm (2.17 in)	
	2: Cylindrical	Ød x h = 30 mm (1.18 in) x 40 mm (1.57 in)	
$h \downarrow \underline{\mathscr{O}d}$ $T \qquad T \qquad h \downarrow \underline{\mathscr{O}d}$	3: Spherical- cylindrical	Φd x h = 30 mm (1.18 in) x 40 mm (1.57 in)	
	4: Spherical	Φd = 25 mm (0.98 in) h = 24 mm (0.94 in)	 P_{max.} depends on the weld-ir process 3-A marked and EHEDG
$h \xrightarrow{\sigma_d} T$ $h \xrightarrow{\sigma_d} T$			certified ASME BPE compliance

Туре	Version			Dimensions	;		Technical properties
Туре	VEISIOII	Ød	ΦA	ØΒ	М	h	reclinical properties
APV Inline							
ØB M M Ød Ød U A0018435	DN50	69 mm (2.72 in)	99.5 mm (3.92 in)	82 mm (3.23 in)	2xM8	19 mm (0.75 in)	 P_{max.} = 25 bar (362 psi) 3-A marked and EHEDG certified ASME BPE compliance

Туре	Version		Dimer	nsions			Technical properties
Туре	Version	ΦD	ΦA	ØΒ	h	P _{max.}	
Varivent®	Туре В	31 mm (1.22 in)	105 mm (4.13 in)	-	22 mm (0.87 in)		
	Type F	50 mm (1.97 in)	145 mm (5.71 in)	135 mm (5.31 in)	24 mm (0.95 in)	10 bar	 3-A marked and EHEDG
	Туре N	68 mm (2.67 in)	165 mm (6.5 in)	155 mm (6.1 in)	24.5 mm (0.96 in)	(145 psi)	certified ASME BPE compliance
A0021307							
The VARINLINE [®] housing connection flange is suitable for weld-in into the conical or torispherical head in tanks or vessels with a small diameter (≤ 1.6 m (5.25 ft)) and up to a wall thickness of 8 mm (0.31 in).							

Time	Version		Technical properties		
Туре	Version	ΦD	ΦA	h	rechnical properties
SMS 1147	DN25	32 mm (1.26 in)	35.5 mm (1.4 in)	7 mm (0.28 in)	
ØD	DN38	48 mm (1.89 in)	55 mm (2.17 in)	8 mm (0.31 in)	
	DN51	60 mm (2.36 in)	65 mm (2.56 in)	9 mm (0.35 in)	P _{max.} = 6 bar (87 psi)
1 Cap-nut 2 Sealing ring 3 Counterpart connection					

T-piece, optimized (no welding, no dead legs)

Time		Version	Dime	ensions in mm (i	n)	Technical anencetica
Туре	Version		ΦD	L	s ¹⁾	Technical properties
	Series A	DN10 PN25	13 mm (0.51 in)			
		DN15 PN25	19 mm (0.75 in)			
		DN20 PN25	23 mm (0.91 in)		1.5 mm (0.06 in)	
T-piece for weld-in as per DIN 11865 (series A, B and C)		DN25 PN25	29 mm (1.14 in)			
G3/8"		DN32 PN25	32 mm (1.26 in)			
	Series B	DN13.5 PN25	13.5 mm (0.53 in)		1.6 mm (0.063 in)	
<u>Ø18</u> (0.71) 88		DN17.2 PN25	17.2 mm (0.68 in)	48 mm		 P_{max.} = 25 bar (362 psi) 3-A marked and EHEDG certified for ≥ DN25
		DN21.3 PN25	21.3 mm (0.84 in)	(1.89 in)		 ASME BPE compliance for ≥ DN25
		DN26.9 PN25	26.9 mm (1.06 in)	-		
		DN33.7 PN25	33.7 mm (1.33 in)	-	2 mm (0.08 in)	
	Series C ²⁾	DN12.7 PN25 (½")	12.7 mm (0.5 in)		1.65 mm (0.065 in)	
		DN19.05 PN25 (¾")	19.05 mm (0.75 in)			
		DN25.4 PN25 (1")	25.4 mm (1 in)			
		DN38.1 PN25 (1½")	38.1 mm (1.5 in)			

1) 2) Wall thickness Pipe dimensions as per ASME BPE 2012

Elbow piece, optimized (no welding, no dead legs)

Time	V			Dimer	isions		Taskaisel monorties
Туре	Version -		ΦD	L1	L2 s ¹⁾		Technical properties
	Series A	DN10 PN25	13 mm (0.51 in)	24 ı (0.9		1.5 mm (0.06 in)	
		DN15 PN25	19 mm (0.75 in)	ر 25 (0.98			
		DN20 PN25	23 mm (0.91 in)	27 ı (1.0			
Corner piece for weld-in as per DIN 11865 (series A, B and C)		DN25 PN25	29 mm (1.14 in)	30 i (1.18			
<u>L2</u> <u>G3/8</u> "		DN32 PN25	35 mm (1.38 in)	33 ı (1.3	mm 5 in)		
	Series B	DN13.5 PN25	13.5 mm (0.53 in)	32 ı (1.2)	mm 6 in)	1.6 mm (0.063 in)	
		DN17.2 PN25	17.2 mm (0.68 in)	34 ı (1.34	mm 4 in)		 P_{max.} = 25 bar (362 psi) 3-A marked and EHEDG certified for ≥ DN25
<u>Ø3.1</u> (0.12) (0.12)		DN21.3 PN25	21.3 mm (0.84 in)	36 i (1.4	mm 1 in)		 ASME BPE compliance for ≥ DN25
		DN26.9 PN25	26.9 mm (1.06 in)	29 ı (1.14			
$\frac{\emptyset 4.5}{(0.18)}$		DN33.7 PN25	33.7 mm (1.33 in)	32 ı (1.2)	mm 6 in)	2.0 mm (0.08 in)	
(0.18) (0	Series C	DN12.7 PN25 (½") ²⁾	12.7 mm (0.5 in)	24 i (0.9		1.65 mm (0.065 in)	
		DN19.05 PN25 (¾")	19.05 mm (0.75 in)	25 ı (0.98			
		DN25.4 PN25 (1")	25.4 mm (1 in)	28 I (1.1			
		DN38.1 PN25 (1½")	38.1 mm (1.5 in)	35 ı (1.38			


1) Wall thickness

2) Pipe dimensions as per ASME BPE 2012

Tip shape

The thermal response time, the reduction of the flow cross-section and the mechanical load that occurs in the process are the criteria that matter when selecting the shape of the tip. Advantages of using reduced or tapered thermometer tips:

- A smaller tip shape has less impact on the flow characteristics of the pipe carrying the medium
- The flow characteristics are optimized
- Thermowell stability is increased



It is possible to verify the mechanical loading capacity as a function of the installation and process conditions using the online TW Sizing Module for thermowells in the Endress+Hauser Applicator software → 🗎 33.

Human interface

Operating concept

The device-specific parameters are configured via IO-Link. Special configuration and operating programs are available from various manufacturers for this purpose. The device description file (IODD) is provided for the thermometer.

IO-Link operating concept

Operator-oriented menu structure for user-specific tasks. Guided menus divided by user category:

- Operator
- Maintenance
- Specialist

Efficient diagnostics increase measurement availability

- Diagnostic messages
- Remedial measures
- Simulation options

IODD download

http://www.endress.com/download

- Select **Software** as the media type
- Select Device Driver as the software type Select IO-Link (IODD)
- In the "Text Search" field enter the device name

https://ioddfinder.io-link.com/

Search by

- Manufacturer
- Article number
- Product type

Local operation

There are no operating elements directly on the device. The temperature transmitter is configured via remote operation.

Local display	There are no display elements directly on the device. The measured value and diagnostic messages, for instance, can be accessed via IO-Link.					
Remote operation	IO-Link functions and device-specific parameters are configured via the device's IO-Link communication.					
	Special configuration kits are available, e.g. the FieldPort SFP20. Every IO-Link device can be configured with it.					
	IO-Link devices are typically configured via the automation system (e.g. Siemens TIA Portal + Port Configuration Tool). Parameters for device replacement can be stored in the IO-Link master.					
	Certificates and approvals					
	Current certificates and approvals that are available for the product can be selected via the Product Configurator at www.endress.com:					
	1. Select the product using the filters and search field.					
	2. Open the product page.					
	3. Select Configuration .					
MTBF	For the transmitter: 327 years, according to Siemens Standard SN29500					
Hygiene standard	 EHEDG certification type EL - CLASS I. EHEDG-certified/tested process connections. → 24 3-A Authorization No. 1144, 3-A Sanitary Standard 74-07. Listed process connections. → 24 ASME BPE, declaration of conformity can be ordered for options indicated FDA-compliant All surfaces in contact with the medium are free from materials derived from bovine animals or other livestock (ADI/TSE) 					
Materials in contact with food/product (FCM)	 The materials of the thermometer in contact with food/product (FCM) comply with the following European regulations: (EC) No. 1935/2004, Article 3, paragraph 1, Articles 5 and 17 on materials and articles intended to come into contact with food. (EC) No. 2023/2006 on good manufacturing practice for materials and articles intended to come into contact with food. (EU) No. 10/2011 on plastic materials and articles intended to come into contact with food. 					
CRN approval	The CRN approval is only available for certain thermowell versions. These versions are identified and displayed accordingly during the configuration of the device.					
	Detailed ordering information is available for your nearest sales organization www.addresses.endress.com or in the Download Area under www.endress.com :					
	1. Select the country					
	2. Select Downloads					
	3. In the search area: select Approvals/approval type					
	4. Enter the product code or device					
	5. Start the search					
CRN approval	The CRN approval is only available for certain thermowell versions. Contact the supplier if necessary.					

Material resistance

Material resistance - including resistance of housing - to the following Ecolab cleaning/disinfection agents:

- P3-topax 66
- P3-topactive 200
- P3-topactive 500
- P3-topactive OKTO
- And demineralized water

Ordering information

Detailed ordering information is available for your nearest sales organization www.addresses.endress.com or in the Product Configurator under www.endress.com :

- 1. Click Corporate
- 2. Select the country
- 3. Click Products

4. Select the product using the filters and search field

5. Open the product page

The Configuration button to the right of the product image opens the Product Configurator.

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop


Accessories

All dimensions in mm (in).


Device-specific accessories	Accessories	Description
	Welding boss with sealing taper	 Collar welding boss movable with sealing taper, washer and pressure screw G½" Material of parts in contact with the process 316L, PEEK Max. process pressure 10 bar (145 psi) Order number with pressure screw 51004751 Order number without pressure screw 51004752
	A0048610 1 Pressure screw. 303/304. width across	
	1 Pressure screw, 303/304, width across flats 24 mm	
	2 Washer, 303/304	
	3 Sealing taper, PEEK	
	4 Collar welding boss, 316L	

Accessories	Description
Collar welding boss G ^{1/2} " (80) 10) 10) 10) 10) 10) 10) 10) 1	 Material of parts in contact with the process 316L Order number without pressure screw 51004752
A0020710	

Accessories	Description
Compression fitting	 Movable clamping ring, process connection G¹/₂" Material of compression fitting and parts in contact with the process, 316L Order number TK40-BADA3C (other versions can be configured in the TK40 structure)
A0048609	
2 AF27	



Weld-in adapter



Material	316L (1.4435)					
Roughness µm (µin) process side	≤1.5 (59.1)	≤0.8 (31.5)	≤0.8 (31.5)	≤0.8 (31.5)	≤0.8 (31.5)	≤0.8 (31.5)

Maximum process pressure for the weld-in adapters:


• 25 bar (362 PSI) at maximum 150 °C (302 °F)

■ 40 bar (580 PSI) at maximum 100 °C (212 °F)

Communication-specific accessories

Accessories	Description
	 Mobile configuration tool for all IO-Link devices: Pre-installed device and CommDTMs in FieldCare Pre-installed device and CommDTMs in FieldXpert M12 connection for IO-Link field devices

Coupling



Accessories	Description
 PVC cable, 4 x 0.34 mm² (22 AWG) with M12x1 coupling, elbow plug, screw plug, length 5 m (16.4 ft) IP67 degree of protection Order number 52024216 Voltage: max. 250 V Current carrying capacity: max. 4 A Temperature: -25 to 70 °C 	1 (BN) 2 (WH) 3 (BU) 4 (BK) A0020723
Wire colors: • 1 = BN brown • 2 = WH white • 3 = BU blue • 4 = BK black	

Accessories	Description
 PVC cable, 4 x 0.34 mm² (22 AWG) with M12x1 coupling nut made of epoxy coated zinc, straight socket contact, screw plug, 5 m (16.4 ft) IP67 degree of protection Order number 71217708 Voltage: max. 250 V Current carrying capacity: max. 4 A Temperature: -20 to 105 °C 	1 (BN) 2 (WH) 3 (BU) 4 (BK) A0020725
Wire colors: • 1 = BN brown • 2 = WH white • 3 = BU blue • 4 = BK black	

Adapter cables

If a TMR3x is replaced by a TM311, the pin assignment must be changed, as the IO-Link standard requires another assignment than that used in TMR3x devices. Either the wiring is changed in the cabinet or the adapter cable is used for the pin assignment between the device and the existing wiring.

Accessories	Description
 Cable: PVC; 2-pin; 2 × 0.34 mm² (AWG22) shielded Cable length ~ 100 mm (3.94 in) without socket and connector Color: black Connector 1: M12, 4-pin, A-coded, socket, straight Connector 2: M12, 4-pin, A-coded, connector, straight 	
 Metal parts: stainless steel Voltage: max. 60 V_{DC} Current carrying capacity: max. 4 A Degree of protection: IP66, IP67 and IP69 in accordance with IEC 60529 (when connected); NEMA 6P Temperature: -40 to +85 °C (-40 to +185 °F) Order number 71449142 	$A M12 \text{ socket} \\ B M12 \text{ connector} \\ L 200 \text{ mm} (7.87 \text{ in}) \\ \end{bmatrix} $

Service-specific accessories	Accessories	Description
	Applicator	 Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum measuring device: e.g. pressure loss, accuracy or process connections. Graphic illustration of the calculation results
		Administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.
		Applicator is available: Via the Internet: https://portal.endress.com/webapp/applicator

Accessories	Description	
Configurator	 Product Configurator - the tool for individual product configuration Up-to-the-minute configuration data Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language Automatic verification of exclusion criteria Automatic creation of the order code and its breakdown in PDF or Excel output format Ability to order directly in the Endress+Hauser Online Shop 	
	The Configurator is available on the Endress+Hauser website at: www.endress.com -> Click "Corporate" -> Select your country -> Click "Products" -> Select the product using the filters and search field -> Open product page -> The "Configure" button to the right of the product image opens the Product Configurator.	
Accessories	Description	
W@M	Life cycle management for your plant W@M offers assistance with a wide range of software applications over the entire process: from planning and procurement to the installation, commissioning and operation of the measuring devices. All the relevant information is available for every measuring device over the entire life cycle, such as the device status, device- specific documentation, spare parts etc. The application already contains the data of your Endress+Hauser device. Endress+Hauser also takes care of maintaining and updating the data records. W@M is available: Via the Internet: www.endress.com/lifecyclemanagement	

System components

Accessories	Description	
IO-Link master BL20	IO-Link master from Turck for DIN rails supports PROFINET, EtherNet/IP and Modbus TCP. With web server for easy configuration.	
Accessories	Description	
RIA16 field indicator	The field indicator presents the analog measuring signal on the display. The LC display shows the current measured value in digital form and as a bar graph indicating a limit value violation. The indicator is looped into the 4 to 20 mA circuit and gets the required energy from there.	
	For details, see Technical Information TI00144R	
Accessories	Description	
RIA15 field indicator	Field indicator for looping into 4 to 20 mA, panel mounting	
	For details, see Technical Information TI00143K	
Accessories	Description	
RIA14 field indicator	Field indicator for looping into 4 to 20 mA, optionally available with Ex d approval.	
	For details, see document TI00143R	
Accessories	Description	
RN22/RN42	RN221: 1- or 2-channel active barrier for separation of 0/4 to 20 mA standard signal circuits, optionally available as a signal duplicator, 24 V DC. HART- transparent RN42: 1-channel active barrier with wide range power supply for safe separation of 0/4 to 20 mA standard signal circuits, HART-transparent For details • Technical Information RN22 -> TI01515K • Technical Information RN42 -> TI01584K	

Documentation

The following document types are available on the product pages and in the download area of the Endress+Hauser website (www.endress.com/downloads):

Purpose and content of the document
Planning aid for your device The document contains all the technical data on the device and provides an overview of the accessories and other products that can be ordered for the device.
Guide that takes you quickly to the 1st measured value The Brief Operating Instructions contain all the essential information from incoming acceptance to initial commissioning.
Your comprehensive reference The Operating Instructions contain all the information that is required in various phases of the life cycle of the device: from product identification, incoming acceptance and storage, to mounting, connection, operation and commissioning through to troubleshooting, maintenance and disposal.
Reference for your parameters The document provides a detailed explanation of each individual parameter. The description is aimed at those who work with the device over the entire life cycle and perform specific configurations.
Depending on the approval, the following Safety Instructions (XA) are supplied with the device. They are an integral part of the Operating Instructions. The nameplate indicates the Safety Instructions (XA) that are
Additional documents are supplied depending on the device version ordered: Always comply strictly with the instructions in the supplementary documentation. The supplementary documentation is an integral part of the device documentation.

Registered trademarks

ð IO-Link

is a registered trademark of the IO-Link company group.



www.addresses.endress.com

