Photocouplers Photorelay

TLP241BP, TLP241BPF

1. Applications

- Heating, ventilation and air conditioning (HVAC)
- Factory Automation (FA)
- Battery Management System (BMS) (Non-Automotive)
- Mechanical relay replacements

2. General

The TLP241BP and TLP241BPF photorelay consist of a photo MOSFET optically coupled to an infrared light emitting diode. They are housed in a 4-pin DIP package. They provide an isolation voltage of 5000 Vrms, making them suitable for applications that require reinforced insulation.TLP241BP has over temperature protection (OTP) and over voltage protection (OVP). So it contributes to reliability of equipment.

3. Features

- (1) Protection: Over Temperature Protection 145°C (typ.), Over Voltage Protection
- (2) Normally opened (1-Form-A)
- (3) OFF-state output terminal voltage: 80 V (min)
- (4) Trigger LED current: 3 mA (max)
- (5) ON-state current: 1.4 A (max)
- (6) ON-state resistance: $280 \text{ m}\Omega \text{ (max)}$
- (7) Isolation voltage: 5000 Vrms (min)
- (8) Halogen-free

For details, see "Devices in Halogen-Free Resin Packages" at the end of this datasheet.


- (9) Safety standards
 - UL-recognized: UL 1577, File No.E67349
 - cUL-recognized: CSA Component Acceptance Service No.5A File No.E67349
 - VDE-approved: EN 60747-5-5 (Note 1)

Note 1: When an EN 60747-5-5 approved type is needed, please designate the Option (D4).

4. Mechanical Parameters


Characteristics	7.62-mm Pitch TLP241BP	10.16-mm Pitch TLP241BPF	Unit
Creepage distances	7.0 (min)	8.0 (min)	mm
Clearance distances	7.0 (min)	8.0 (min)	
Internal isolation thickness	0.4 (min)	0.4 (min)	

5. Packaging (Note)




Note: Through-hole type: TLP241BP, TLP241BPF Lead forming option: (LF1), (LF4), (LF5) Taping option: (TP1), (TP4), (TP5)

6. Pin Assignment



7. Internal Circuit



8. Absolute Maximum Ratings (Note) (Unless otherwise specified, $T_a = 25$ °C)

	Characteristics		Symbol	Note	Rating	Unit
LED	Input forward current		١ _F		20	mA
	Input forward current derating	$(T_a \ge 97 \ ^\circ C)$	$\Delta I_F / \Delta T_a$		-0.71	mA/°C
	Input reverse voltage		V _R		6	V
	Input power dissipation		PD		40	mW
	Input power dissipation derating	$(T_a \ge 97 \ ^\circ C)$	$\Delta P_D / \Delta T_a$		-1.43	mW/°C
	Junction temperature		Tj		125	°C
Detector	OFF-state output terminal voltage		V _{OFF}		80	V
	ON-state current		I _{ON}		1.4	A
	ON-state current derating	$(T_a \ge 25 \ ^\circ C)$	$\Delta I_{ON} / \Delta T_a$		-14	mA/°C
	ON-state current (pulsed)	(t = 100 ms, Duty = 1/10)	I _{ONP}		4.2	A
	Output power dissipation		Po		550	mW
	Output power dissipation derating	$(T_a \ge 25 \ ^\circ C)$	$\Delta P_0 / \Delta T_a$		-5.5	mW/°C
	Junction temperature		Tj		125	°C
Common	Storage temperature		T _{stg}		-55 to 125	°C
	Operating temperature		T _{opr}		-40 to 110	°C
	Lead soldering temperature	(10 s)	T _{sol}		260	°C
	Isolation voltage	AC, 60 s, R.H. ≤ 60 %	BVS	(Note 1)	5000	Vrms

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Note 1: This device is considered as a two-terminal device: Pins 1 and 2 are shorted together, and pins 3 and 4 are shorted together.

9. Recommended Operating Conditions (Note)

Characteristics	Symbol	Note	Min	Тур.	Max	Unit
Input forward current	١ _F		7	_	14	mA

Note: The recommended operating conditions are given as a design guide necessary to obtain the intended performance of the device. Each parameter is an independent value. When creating a system design using this device, the electrical characteristics specified in this data sheet should also be considered.

10. Electrical Characteristics (Unless otherwise specified, $T_a = 25$ °C)

	Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
LED	Input forward voltage	V _F		I _F = 10 mA	1.50	1.65	1.80	V
	Input reverse current	I _R		V _R = 6 V		_	10	μA
	Input capacitance	Ct		V = 0 V, f = 1 MHz	_	50	_	pF
Detector	OFF-state current	I _{OFF}		V _{OFF} = 40 V		_	1	μA
	OFF-state current	I _{OFF}		V _{OFF} = 60 V		_	10	μA
	Output capacitance	C _{OFF}		V = 0 V, f = 1 MHz	_	130	_	pF
	Over voltage clamp	V _{OVC}		I _F = 0 mA, I _{OFF} = 10 mA, t = 10 μs	80	_	100	V

11. Coupled Electrical Characteristics (Unless otherwise specified, $T_a = 25$ °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Trigger LED current	I _{FT}		I _{ON} = 1.0 A	_	1	3	mA
Return LED current	I _{FC}		I _{OFF} = 10 μA	0.01		_	
ON-state resistance	R _{ON}		I _{ON} = 1.4 A, I _F = 10 mA, t < 1 s	_	0.16	0.28	Ω
Thermal shutdown temperature	T _{SD}		I _{OFF} = 10 μA, I _F = 10 mA		145		°C


12. Isolation Characteristics (Unless otherwise specified, $T_a = 25$ °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Total capacitance (input to output)	CS	(Note 1)	V _S = 0 V, f = 1 MHz		0.8	—	pF
Isolation resistance	R _S	(Note 1)	V_S = 500 V, R.H. \leq 60 %	10 ¹²	1014	_	Ω
Isolation voltage	BVS	(Note 1)	AC, 60 s	5000	_	_	Vrms

Note 1: This device is considered as a two-terminal device: Pins 1 and 2 are shorted together, and pins 3 and 4 are shorted together.

13. Switching Characteristics (Unless otherwise specified, $T_a = 25$ °C)

Characteristics	Symbol	Note	Test Condition	Min	Тур.	Max	Unit
Turn-on time	t _{ON}		See Fig. 13.1.		0.4	1.4	ms
Turn-off time	t _{OFF}		R_{L} = 200 Ω, V_{DD} = 20 V, I_{F} = 10 mA	_	0.03	0.5	






Fig. 13.1 Switching Time Test Circuit and Waveform

14. Characteristics Curves (Note)






Fig. 14.6 I_{ON} - V_{ON}

Fig. 14.5 IF - VF







Note: The above characteristics curves are presented for reference only and not guaranteed by production test, unless otherwise noted.

15. Protection Operation


15.1. Over temperature protection

To prevent damage due to temperature rise, the outputs are turned off when the sensing chip in control circuit exceeds the over Thermal shutdown temperature (T_{SD}). Once this protection activate, the output turn to latch off statement and turn off regardless sensing chip temperature. To reset this statement, you should set LED input forward current zero once.

15.2. Over voltage protection

Over voltage protection is a function that when over voltage surge applied, output part clamps and keeps voltage defference between itself. This protection is only for short time surge. So if it is long time applied and exceeds V_{OVC} , it might break.

15.3. Timing Diagrams





Note: $10\mu s$ in this figure is reference value

16. Case with reflow


When using soldering reflow.

The soldering temperature profile is based on the package surface temperature.

(See the figure shown below, which is based on the package surface temperature.)

Reflow soldering must be performed once or twice.

The mounting should be completed with the interval from the first to the last mountings being 2 weeks.



	Symbol	Min	Max	Unit
Preheat temperature	Ts	150	200	°C
Preheat time	ts	60	120	s
Ramp-up rate (T_L to T_P)			3	°C/s
Liquidus temperature	TL	217		°C
Time above T _L	tL	60	150	s
Peak temperature	Τ _Ρ		260	°C
Time during which T_c is between (T_P – 5) and T_P	tp		30	s
Ramp-down rate $(T_P \text{ to } T_L)$			6	°C/s

An Example of a Temperature Profile When Lead(Pb)-Free Solder Is Used

• When using soldering flow

Preheat the device at a temperature of 150 $^{\circ}\mathrm{C}$ (package surface temperature) for 60 to 120 seconds. Mounting condition of 260 $^{\circ}\mathrm{C}$ within 10 seconds is recommended.

Flow soldering must be performed once.

 When using soldering Iron Complete soldering within 10 seconds for lead temperature not exceeding 260 °C or within 3 seconds not exceeding 350 °C

Heating by soldering iron must be done only once per lead.

16.1. Precautions for General Storage

- Avoid storage locations where devices may be exposed to moisture or direct sunlight.
- Follow the precautions printed on the packing label of the device for transportation and storage.
- Keep the storage location temperature and humidity within a range of 5 $^\circ C$ to 35 $^\circ C$ and 45 % to 75 %, respectively.
- Do not store the products in locations with poisonous gases (especially corrosive gases) or in dusty conditions.
- Store the products in locations with minimal temperature fluctuations. Rapid temperature changes during storage can cause condensation, resulting in lead oxidation or corrosion, which will deteriorate the solderability of the leads.
- When restoring devices after removal from their packing, use anti-static containers.
- Do not allow loads to be applied directly to devices while they are in storage.
- If devices have been stored for more than two years under normal storage conditions, it is recommended that you check the leads for ease of soldering prior to use.

17. Ordering Information (Example of Item Name)

Item Name	Packaging (Note 1)	VDE Option	Packing (MOQ)
TLP241BP(E	ТН		Magazine (100 pcs)
TLP241BP(LF1,E	LF1		Magazine (100 pcs)
TLP241BP(LF5,E	LF5		Magazine (100 pcs)
TLP241BP(TP1,E	LF1		Tape and reel (1500 pcs)
TLP241BP(TP5,E	LF5		Tape and reel (1500 pcs)
TLP241BP(D4,E	TH	EN 60747-5-5	Magazine (100 pcs)
TLP241BP(D4LF1,E	LF1	EN 60747-5-5	Magazine (100 pcs)
TLP241BP(D4LF5,E	LF5	EN 60747-5-5	Magazine (100 pcs)
TLP241BP(D4TP1,E	LF1	EN 60747-5-5	Tape and reel (1500 pcs)
TLP241BP(D4TP5,E	LF5	EN 60747-5-5	Tape and reel (1500 pcs)
TLP241BPF(E	TH, Wide forming		Magazine (100 pcs)
TLP241BPF(LF4,E	LF4, Wide forming		Magazine (100 pcs)
TLP241BPF(TP4,E	LF4, Wide forming		Tape and reel (1000 pcs)
TLP241BPF(D4,E	TH, Wide forming	EN 60747-5-5	Magazine (100 pcs)
TLP241BPF(D4LF4,E	LF4, Wide forming	EN 60747-5-5	Magazine (100 pcs)
TLP241BPF(D4TP4,E	LF4, Wide forming	EN 60747-5-5	Tape and reel (1000 pcs)

Note 1: TH: Through-hole, LF: Lead forming for surface mount

18. Devices in Halogen-Free Resin Packages

 \cdot This product is Halogen-Free

Toshiba Electronic Devices & Storage Corporation ("Toshiba") defines a "Halogen-Free resin semiconductor product" as a semiconductor product in which:

- (1) the encapsulating resins do not contain any of the following elements: bromine (Br), chlorine (Cl) and antimony (Sb), respectively, in an amount exceeding 0.09 weight percent, and do not contain chlorine and bromine in an aggregate amount exceeding 0.15 weight percent of the encapsulating resins, and/or
- (2) the resin portion(s) in printed circuit boards do not contain any of the following elements: bromine, chlorine and antimony, respectively, in an amount exceeding 0.09 weight percent, and do not contain chlorine and bromine in an aggregate amount exceeding 0.15 weight percent of the each resin portion(s) in printed circuit boards.

For avoidance of doubt, "Halogen-Free resin semiconductor product" does not mean, and Toshiba does not make any warranty of any kind, that said semiconductor product is entirely free of antimony or of any of the following elements of the halogen family: bromine, chlorine, iodine (I), fluorine (F) and astatine (At).


In addition, a Halogen-Free resin semiconductor product may contain antimony and/or any of the elements of the halogen family as mentioned in the above paragraph in one or more portion(s) of the semiconductor product other than the encapsulating resins and the resin portion(s) in printed circuit boards.

The information provided herein is accurate as of the date that it was provided, to the best of the knowledge and belief of the Toshiba Electronic Devices & Storage Corporation ("Toshiba"), Toshiba bases such knowledge and belief on information provided by third parties, and Toshiba makes no representation or warranty as to the accuracy of such third party information. Toshiba has taken and will continue to take, reasonable steps to provide accurate information to its customers, but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals.

Package Dimensions

TLP241BP, TLP241BPF

Unit: mm




Weight: 0.26 g (typ.)

Package Name(s) TOSHIBA: 11-5B2S



TLP241BP, TLP241BPF


Unit: mm



Weight: 0.25 g (typ.)

Package Name(s) TOSHIBA: 11-5B201S

Unit: mm




Weight: 0.25 g (typ.)

Package Name(s) TOSHIBA: 11-5B205S



TLP241BP, TLP241BPF

Unit: mm




Weight: 0.26 g (typ.)

Package Name(s)	
TOSHIBA: 11-5B202S	

TLP241BP, TLP241BPF

Unit: mm



Weight: 0.25 g (typ.)

Package Name(s) TOSHIBA: 11-5B204S

RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").

Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, lifesaving and/or life supporting medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, and devices related to power plant.

IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your TOSHIBA sales representative or contact us via our website.

- · Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor. Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.

TOSHIBA ELECTRONIC DEVICES & STORAGE CORPORATION

https://toshiba.semicon-storage.com/