



Product Change Notification / MAAN-07HYRJ408

Date:

04-Jan-2024

Product Category:

8-Bit Microcontrollers

PCN Type:

Manufacturing Change

Notification Subject:

CCB 6332 Final Notice: Qualification of MTAI as a new final test site for selected ATTINY13x device family available in 8L SOIC (0.15 in) and 8L SOIJ (0.208 in) packages.

Affected CPNs:

[MAAN-07HYRJ408_Affected_CPN_01042024.pdf](#)

[MAAN-07HYRJ408_Affected_CPN_01042024.csv](#)

Notification Text:

PCN Status:Final Notification

PCN Type:Manufacturing Change

Microchip Parts Affected:Please open one of the files found in the Affected CPNs section.

Note: For your convenience Microchip includes identical files in two formats (.pdf and .xls)

Description of Change:Qualification of MTAI as a new final test site for selected ATTINY13x device family available in 8L SOIC (0.15 in) and 8L SOIJ (0.208 in) packages.

Pre and Post Change Summary:

For 8L SOIC Package:

	Pre Change	Post Change
--	------------	-------------

Final Test Site		Amkor Technology Philippine (P1/P2), INC. (ANAP)	Lingsen Precision Industries, LTD. (LPI)	Microchip Technology Thailand (MTAI)
Base Quantity Multiple (BQM)	Tape and Reel	4000	4000	4000
	Tube	100	100	100
Pin 1 Orientation	Tape and Reel	Quadrant 1	Quadrant 1	Quadrant 1
	Tube	See Pre and Post Change comparison		
Carrier Tape		Minimal dimensional changes. See Pre and Post Change Summary for comparison.		
Cover Tape				
Plastic Reel				
See Pre and Post Change Summary for comparison.				

For 8L SOIJ Package:

		Pre Change		Post Change
Final Test Site		Amkor Technology Philippine (P1/P2), INC. (ANAP)	Lingsen Precision Industries, LTD. (LPI)	Microchip Technology Thailand (MTAI)
Base Quantity Multiple (BQM)	Tape and Reel	2000	2000	2000
	Tube	95	95	90
Pin 1 Orientation	Tape and Reel	Quadrant 1	Quadrant 1	Quadrant 1
	Tube	See Pre and Post Change comparison		
Carrier Tape		With minor dimensional changes. See Pre and Post Change Summary for comparison.		
Cover Tape				
Plastic Reel				
See Pre and Post Change Summary for comparison.				

Impacts to Data Sheet:None

Change Impact:None

Reason for Change:To improve manufacturability by qualifying MTAI as new final test site.

Change Implementation Status:In Progress

Estimated First Ship Date:February 5, 2024 (date code: 2406)

Note: Please be advised that after the estimated first ship date customers may receive pre and post change parts.

Time Table Summary:

	October 2023					>	January 2024					February 2024				
Workweek	4 0	4 1	4 2	4 3	4 4		0 1	0 2	0 3	0 4	0 5	0 6	0 7	0 8	0 9	1 0
Initial PCN Issue Date		x														
Qual Report Availability							x									
Final PCN Issue Date							x									
Estimated Implementation Date												x				

Method to Identify Change:Traceability code

Qualification Report:Please open the attachments included with this PCN labeled as PCN_#_Qual_Report.

Revision History:October 12, 2023: Issued initial notification.

January 4, 2024: Issued final notification. Attached the Qualification Report. Provided estimated first ship date to be on February 5, 2024.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

Attachments:

[PCN_MAAN-07HYRJ408_Pre_and_Post_Change_Summary.pdf](#)

[PCN_MAAN-07HYRJ408_Qual_Report.pdf](#)

Please contact your local **Microchip sales office** with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.

Affected Catalog Part Numbers (CPN)

- ATTINY13A-SS7
- ATTINY13A-SN
- ATTINY13A-SS7R
- ATTINY13A-SNR
- ATTINY13-20SSU
- ATTINY13V-10SSU
- ATTINY13V-10SU
- ATTINY13-20SU
- ATTINY13-20SSUR
- ATTINY13V-10SSUR
- ATTINY13V-10SUR
- ATTINY13-20SUR


CCB 6332

Pre and Post Change Summary

PCN #: MAAN-07HYRJ408











A Leading Provider of Smart, Connected and Secure Embedded Control Solutions







SMART | CONNECTED | SECURE



Tape and Reel - 8L SOIC Package

	ANAP	LPI	MTAI								
BQM (Base Quantity Multiple)	4000	4000	4000								
Pin 1 orientation	MSL 1 UPPER LEFT  MSL 2 UPPER LEFT 	Upper left corner <table><tr><th>Media</th><th>Pin1 Side</th></tr><tr><td>T/R</td><td>  Carrier Tape 12 34 Quadrant 1 </td></tr></table>	Media	Pin1 Side	T/R	 Carrier Tape 12 34 Quadrant 1	<table><tr><th>Media</th><th>Pin1 Side</th></tr><tr><td>T/R</td><td>  Carrier Tape 12 34 Quadrant 1 </td></tr></table>	Media	Pin1 Side	T/R	 Carrier Tape 12 34 Quadrant 1
Media	Pin1 Side										
T/R	 Carrier Tape 12 34 Quadrant 1										
Media	Pin1 Side										
T/R	 Carrier Tape 12 34 Quadrant 1										

Carrier Tape – T/R- 8L SOIC Package




ANAP		LPI		MTAI	
MSL 1 					
MSL 2 					
Plant	W (mm.)	P (mm.)	A0 (mm.)	B0 (mm.)	K0 (mm.)
ANAP	12.00 +/- 0.3	8.00 +/- 0.1	6.40 +/- 0.1	5.20 +/- 0.1	2.10 +/- 0.1
LPI	12.00 +0.3/-0.1	8.00	6.50 +/- 0.1	5.20 +/- 0.1	2.10 +/- 0.1
MTAI	12.00 +/- 0.3	8.00 +/- 0.1	6.40 +/- 0.1	5.20 +/- 0.1	2.10 +/- 0.1

Reel – T/R - 8L SOIC Package



ANAP	LPI	MTAI
MSL 1 & 2 		

Plant	Colour	Diameter	Hub Dia	W1	W2
ANAP	White	329.99mm	100mm	13.5mm	17.5mm
LPI	White	330mm	102mm	4.4mm 8.4mm	7.1mm 11.1mm
MTAI	Dark Blue	330mm	100mm	12.40mm	18.40mm

Cover Tape – T/R - 8L SOIC Package

ANAP	LPI	MTAI												
														
<table><tr><td>Width</td><td>9.2 mm</td></tr><tr><td>Thickness</td><td>0.053mm</td></tr></table>	Width	9.2 mm	Thickness	0.053mm	<table><tr><td>Width</td><td>9.2mm</td></tr><tr><td>Thickness</td><td>0.048mm</td></tr></table>	Width	9.2mm	Thickness	0.048mm	<table><tr><td>Width</td><td>9.05mm</td></tr><tr><td>Thickness</td><td>0.050mm</td></tr></table>	Width	9.05mm	Thickness	0.050mm
Width	9.2 mm													
Thickness	0.053mm													
Width	9.2mm													
Thickness	0.048mm													
Width	9.05mm													
Thickness	0.050mm													

Antistatic Shielding/Moisture barrier Bag - T/R - 8L SOIC Package

ANAP	LPI	MTAI												
MSL 1  <table><tr><td>Length</td><td>457.2 mm</td></tr><tr><td>Width</td><td>381 mm</td></tr></table>	Length	457.2 mm	Width	381 mm	 <table><tr><td>Length</td><td>450 mm</td></tr><tr><td>Width</td><td>420 mm</td></tr></table>	Length	450 mm	Width	420 mm	 <table><tr><td>Length</td><td>420 mm</td></tr><tr><td>Width</td><td>370 mm</td></tr></table>	Length	420 mm	Width	370 mm
Length	457.2 mm													
Width	381 mm													
Length	450 mm													
Width	420 mm													
Length	420 mm													
Width	370 mm													

Desiccant – T/R - 8L SOIC Package

ANAP	LPI	MTAI
MSL 1 N/A		N/A
MSL 2		




Carton Box – T/R - 8L SOIC Package

ANAP	LPI	MTAI					
MSL 1 & MSL 2 Length: 370 mm Width: 350 mm Height: 53 mm Clear Tape Barcode Label 	 37.0x38.0x11.0 cm (2 inner box per 1 outer box) 37.0x38.0x22.5 cm (4 inner box per 1 outer box) 37.0x39.0x39.0 cm (8 inner box per 1 outer box) 42.0x66.0x39.0 cm (11 inner box per 1 outer box)	 <table><tr><td>365 x 380 x 395 mm</td></tr><tr><td>355 x 355 x 28 mm</td></tr><tr><td>355 x 355 x 40 mm</td></tr><tr><td>355 x 355 x 60 mm</td></tr><tr><td>355 x 355 x 165 mm</td></tr></table>	365 x 380 x 395 mm	355 x 355 x 28 mm	355 x 355 x 40 mm	355 x 355 x 60 mm	355 x 355 x 165 mm
365 x 380 x 395 mm							
355 x 355 x 28 mm							
355 x 355 x 40 mm							
355 x 355 x 60 mm							
355 x 355 x 165 mm							




Tube - 8L SOIC Package

	ANAP	LPI	MTAI
BQM (Base Quantity Multiple)	100	100	100

Pin Orientation - Tube - 8L SOIC Package

ANAP	LPI	MTAI						
MSL 1 LOWER LEFT REFERENCE TO TUBE MARKING 	Pin 1 side Green Opposite side White 	 <table border="1"> <thead> <tr> <th>Media</th><th>Pin1 Side</th><th>Opposite Side</th></tr> </thead> <tbody> <tr> <td>TUBE</td><td>White</td><td>Black</td></tr> </tbody> </table>	Media	Pin1 Side	Opposite Side	TUBE	White	Black
Media	Pin1 Side	Opposite Side						
TUBE	White	Black						
MSL 2 UPPER RIGHT REFERENCE TO TUBE MARKING 								

Tube - 8L SOIC Package

ANAP	 <table><tr><td>Length</td><td>20.45 in</td></tr><tr><td>Color</td><td>Clear Blue</td></tr></table>	Length	20.45 in	Color	Clear Blue	 <table><tr><td>Color</td><td>Clear Blue</td></tr></table>	Color	Clear Blue
Length	20.45 in							
Color	Clear Blue							
Color	Clear Blue							
LPI	 <table><tr><td>Length</td><td>20.4 in</td></tr><tr><td>Color</td><td>Clear</td></tr></table>		Length	20.4 in	Color	Clear		
Length	20.4 in							
Color	Clear							
MTAI	 <table><tr><td>Length</td><td>20.5 in</td></tr><tr><td>Color</td><td>Clear</td></tr></table>		Length	20.5 in	Color	Clear		
Length	20.5 in							
Color	Clear							

Antistatic Shielding/Moisture barrier Bag - Tube- 8L SOIC Package

ANAP	LPI	MTAI										
MSL 1  <table><tr><td>Length</td><td>635 mm</td></tr><tr><td>Width</td><td>304 mm</td></tr></table>	Length	635 mm	Width	304 mm	Antistatic Shielding Bag 770x210x0.08mm Moisture Barrier Bag 760x150x0.15mm 255*765*0.15mm 	<table><tr><th>P/N</th><th>WIDTH</th><th>LENGTH</th></tr><tr><td>DY3650</td><td>160</td><td>650</td></tr></table> SSB 	P/N	WIDTH	LENGTH	DY3650	160	650
Length	635 mm											
Width	304 mm											
P/N	WIDTH	LENGTH										
DY3650	160	650										
MSL 2  <table><tr><td>Length</td><td>762 mm</td></tr><tr><td>Width</td><td>203.2 mm</td></tr></table>	Length	762 mm	Width	203.2 mm								
Length	762 mm											
Width	203.2 mm											





Desiccant – Tube - 8L SOIC Package

ANAP	LPI	MTAI
MSL 1 N/A		N/A
MSL 2 		




Carton Box - Tube - 8L SOIC Package

ANAP	LPI	MTAI						
MSL 1 & MSL 2  Length: 129 mm Width: 565 mm Height: 80 mm	 28.0x60.0x11.0 cm (2 inner box per 1 outer box) 43.0x60.0x19.0 cm (6 inner box per 1 outer box)	 <table><tr><td>150 x 640 x 55 mm</td></tr><tr><td>150 x 640 x 100 mm</td></tr><tr><td>150 x 640 x 140 mm</td></tr><tr><td>280 x 630 x 110 mm</td></tr><tr><td>280 x 630 x 155 mm</td></tr><tr><td>280 x 630 x 200 mm</td></tr></table>	150 x 640 x 55 mm	150 x 640 x 100 mm	150 x 640 x 140 mm	280 x 630 x 110 mm	280 x 630 x 155 mm	280 x 630 x 200 mm
150 x 640 x 55 mm								
150 x 640 x 100 mm								
150 x 640 x 140 mm								
280 x 630 x 110 mm								
280 x 630 x 155 mm								
280 x 630 x 200 mm								


Tape and Reel - 8L SOIJ Package

	ANAP	LPI	MTAI
BQM (Base Quantity Multiple)	2000	2000	2000
Pin 1 orientation	MSL 1  MSL 2 	Quadrant 1 	Quadrant 1 

Carrier Tape – T/R - 8L SOIJ Package

ANAP		LPI		MTAI	
MSL 1 & MSL 2					
					
Plant	W (mm.)	P (mm.)	A0 (mm.)	B0 (mm.)	K0 (mm.)
ANAP	16.00 +0.3/-0.1	12.00 +/- 0.1	8.45 +/- 0.1	5.70 +/- 0.1	2.35 +/- 0.1
LPI	16.00	12.00	8.450 +/- 0.1	5.70 +/- 0.1	2.35 +/- 0.1
MTAI	16.00	12.00	8.30 +/- 0.1	5.70 +/- 0.1	2.30 +/- 0.1

Reel – T/R - 8L SOIJ Package

ANAP	LPI	MTAI
MSL 1 & 2 		

Plant	Colour	Diameter	W1	W2
ANAP	White	329.99mm	17mm	19.4mm
LPI	White	330mm	4.4mm 8.4mm	7.1mm 11.1mm
MTAI	Dark Blue	330mm	16.40mm	22.40mm

Cover Tape – T/R - 8L SOIJ Package

ANAP	LPI	MTAI																
0.053 ± 0.005 HEAT ACTIVATED ADHESIVE THIS SIDE 76.2MM (3.0 INCHES) NOMINAL INSIDE CORE DIAMETER WIDTH "W" NOTE: 1. STANDARD ROLL TO CONTAIN 300 METERS OF SPICE-FREE MATERIAL. 2. ROLLS OTHER THAN THE STANDARD LENGTH WILL BE DESIGNATED BY ADDING THE LENGTH TO THE EXISTING PART NUMBER. EXAMPLE: ABX0133-XXX, WHERE XXX EQUALS LENGTH 3. MATERIAL: POLYESTER FILM WITH ANTISTATIC AND ADHESIVE COATINGS 4. COLOR: GRAY <table><tr><th>PART NO.</th><th>WIDTH "W"</th></tr><tr><td>ABX0133</td><td>13.3 ±0.10mm</td></tr></table> <table><tr><td>Width</td><td>13.33 mm</td></tr><tr><td>Thickness</td><td>0.053mm</td></tr></table>	PART NO.	WIDTH "W"	ABX0133	13.3 ±0.10mm	Width	13.33 mm	Thickness	0.053mm	<table><tr><td>Width</td><td>13.3 mm</td></tr><tr><td>Thickness</td><td>0.048mm</td></tr></table>	Width	13.3 mm	Thickness	0.048mm	TOP VIEW Detail A 77 ±1.0 mm 100 ±1.0 mm W Cover Tape Width SIDE VIEW <table><tr><td>Width</td><td>13.3 mm</td></tr><tr><td>Thickness</td><td>0.050mm</td></tr></table>	Width	13.3 mm	Thickness	0.050mm
PART NO.	WIDTH "W"																	
ABX0133	13.3 ±0.10mm																	
Width	13.33 mm																	
Thickness	0.053mm																	
Width	13.3 mm																	
Thickness	0.048mm																	
Width	13.3 mm																	
Thickness	0.050mm																	

Antistatic Shielding/Moisture barrier Bag - T/R - 8L SOIJ Package

ANAP	LPI	MTAI												
MSL 1  <table><tr><td>Length</td><td>457.2 mm</td></tr><tr><td>Width</td><td>381 mm</td></tr></table>	Length	457.2 mm	Width	381 mm	 <table><tr><td>Length</td><td>450 mm</td></tr><tr><td>Width</td><td>420 mm</td></tr></table>	Length	450 mm	Width	420 mm	 <table><tr><td>Length</td><td>370 mm</td></tr><tr><td>Width</td><td>420 mm</td></tr></table>	Length	370 mm	Width	420 mm
Length	457.2 mm													
Width	381 mm													
Length	450 mm													
Width	420 mm													
Length	370 mm													
Width	420 mm													

Desiccant – T/R - 8L SOIJ Package




ANAP	LPI	MTAI
MSL 1		N/A
MSL 2		



Tube - 8L SOIJ Package

	ANAP	LPI	MTAI
BQM (Base Quantity Multiple)	95	95	90

Tube - 8L SOIJ Package

ANAP	<table><tr><td>Length</td><td>20.866 in</td></tr><tr><td>Color</td><td>Clear Blue</td></tr></table>	Length	20.866 in	Color	Clear Blue	<table><tr><td>Length</td><td>20.866 in</td></tr><tr><td>Color</td><td>Clear Blue</td></tr></table>	Length	20.866 in	Color	Clear Blue
Length	20.866 in									
Color	Clear Blue									
Length	20.866 in									
Color	Clear Blue									
LPI	<table><tr><td>Length</td><td>20.86 in</td></tr><tr><td>Color</td><td>Clear</td></tr></table>		Length	20.86 in	Color	Clear				
Length	20.86 in									
Color	Clear									
MTAI	<table><tr><td>Length</td><td>20 in</td></tr><tr><td>Color</td><td>Clear</td></tr></table>		Length	20 in	Color	Clear				
Length	20 in									
Color	Clear									

Antistatic Shielding/Moisture barrier Bag - Tube- 8L SOIJ Package


ANAP	LPI	MTAI												
MSL 1  <table><tr><td>Length</td><td>635 mm</td></tr><tr><td>Width</td><td>304 mm</td></tr></table>	Length	635 mm	Width	304 mm	 <table><tr><td>Length</td><td>765 mm</td></tr><tr><td>Width</td><td>255 mm</td></tr></table>	Length	765 mm	Width	255 mm	 <table><tr><td>Length</td><td>160 mm</td></tr><tr><td>Width</td><td>650 mm</td></tr></table>	Length	160 mm	Width	650 mm
Length	635 mm													
Width	304 mm													
Length	765 mm													
Width	255 mm													
Length	160 mm													
Width	650 mm													
MSL 2  <table><tr><td>Length</td><td>762 mm</td></tr><tr><td>Width</td><td>203.2 mm</td></tr></table>	Length	762 mm	Width	203.2 mm										
Length	762 mm													
Width	203.2 mm													

Desiccant – Tube - 8L SOIJ Package

ANAP	LPI	MTAI
MSL 1		N/A
MSL 2		



Carton Box - Tube - 8L SOIJ Package

ANAP	LPI	MTAI						
MSL 1 & MSL 2  Length: 129 mm Width: 565 mm Height: 80 mm	  580 x 129 x 80mm 600 x 280 x 105mm 600 x 430 x 188mm	  <table><tr><td>150 x 640 x 55 mm</td></tr><tr><td>150 x 640 x 100 mm</td></tr><tr><td>150 x 640 x 140 mm</td></tr><tr><td>280 x 630 x 110 mm</td></tr><tr><td>280 x 630 x 155 mm</td></tr><tr><td>280 x 630 x 200 mm</td></tr></table>	150 x 640 x 55 mm	150 x 640 x 100 mm	150 x 640 x 140 mm	280 x 630 x 110 mm	280 x 630 x 155 mm	280 x 630 x 200 mm
150 x 640 x 55 mm								
150 x 640 x 100 mm								
150 x 640 x 140 mm								
280 x 630 x 110 mm								
280 x 630 x 155 mm								
280 x 630 x 200 mm								



QUALIFICATION REPORT SUMMARY
RELIABILITY LABORATORY

PCN #: MAAN-07HYRJ408

Date:
December 11, 2023

**Qualification of MTAI as a new final test site for selected
ATTINY13xx device family available in 8L SOIC (0.15 in) and
8L SOIJ (0.208 in) package.**

Purpose: Qualification of MTAI as a new final test site for selected ATTINY13xx device family available in 8L SOIC (0.15 in) and 8L SOIJ (0.208 in) package.

CCB: 6332

Test Name	Test Conditions	Results
Datalog/Bin Comparison	• Compare test numbers, test names, test sequence bin assignments & pass/fail results • Accept if all match or justify the differences	Passed
Site by Site Verification	• Verifies the channel map has the correct site assignments and tester/handler communications work correctly	Passed
Correlation Lot Report	• Yield comparison between systems and test sites. • Accept on yield match within 2%	Passed
Unit to unit parametric correlation	• A full assembly strip characterized on both systems and graphed vs each other & the data sheet limits	Passed
Test Stability Verification	• 50 loop test performed with no datalog delays - Accept on 0 fails	Passed
Parametric test stability verification	• Use Real Time Statistics software.	Passed