

Sharkfin / Vehicular

5G-FR1+WiFi-6E/7+GNSS L1+L2+LMR DM 7-in-1 Antenna

SKF5G72311DMWXXX - 617 to 712!



SKF5G72311DMW1585

Features & Applications:

- Vehicle roof mount, directly on metal plane
- 2x2 MiMo Cellular 5G-FR1 (4G compatible)
- 3x3 MiMo WiFi, DSRC, V2X (WiFi-6E/7 compatible)
- Active GNSS L1+L2/L5 with 28-30dB low noise amplifier
- Removable flexible TETRA, UHF, VHF whip
- Options1:150MHz, 380MHz, 450MHz
- Options2:TETRA, UHF, VHF 3 band whip
- Cable length and connector type per request
- Heavy and light vehicles
- IoT, navigation, tracking

ELECTRICAL SPECIFICATIONS

General Specifications – 5G FR1 + WiFi 6E/7

Antenna type	Nominal Impedance	Polarization	Radiation Pattern	Power Withstanding				DC Ground
Monopole ¹	50Ω	Vertical / Linear	Omni	5G: 45W	WiFi: 25W	Single Band LMR 45W	Tri band LMR: 65W	No

5G FR1 Antennas: 617 – 5925MHz

Port	Frequency (MHz)	617-960	1710-2700	3300-4200	4400-5000	5150-5925
Port 1, 2	VSWR	3:1	2:1	2.5:1	2.5:1	2.5:1
	Avg. Peak Gain (dBi)	2.3	4.6	4.9	5.7	5.4
	Avg. Efficiency (%)	51	54	68	68	62
Isolation ²	Port 1-2 (dB)	10	25	30	40	45

WiFi 6E/7 Antennas: 2400-2500 / 4900-7125MHz

Port	Frequency (MHz)	2400-2500	4900-7125
Port 1,2,3	VSWR	2:1	2.5:1
	Avg. Peak Gain (dBi)	6.0	4.7
	Avg. Efficiency (%)	62	76
Port – Port Isolation ²	Port 1-2 (dB)	10	20
	Port 1-3 (dB)	12	25
	Port 2-3 (dB)	15	30

LMR Antenna: 150-160MHz/380-430MHz/400-512MHz/740-960MHz/150-160&450-512&758-960 MHz

Pulse P/N (7 in 1 Antenna + Whip antenna)		SKF5G72311DM W155	SKF5G72311DM W400	SKF5G72311DM W470	SKF5G72311DM W850	SKF5G72311DM W1585
Pulse P/N (Only Whip antenna)		WLMR155G	WLMR400G	WLMR470G	WLMR850G	WLMR155446850G
Frequency (MHz)		150-160	380-430	400-512	740-960	150-160/450-512/758-960
Whip Antenna Size (MM)		Ø12.8X184mm				Ø12.8X377mm
Port 1	VSWR	3:1	3:1	3:1	3:1	2.5:1
	Avg. Peak Gain (dBi)	1.1	3.0	1.2	2.0	1.2
	Avg. Efficiency (%)	/	55	50	52	42

Notes:

1. Multi-Band Monopoles with built in ground plane, Independent from external ground plane
2. Minimum Isolation (dB)

ELECTRICAL SPECIFICATIONS

GNSS Antenna L1 Band: 1561.098 +/- 2.046MHz, 1575.42 +/- 1.023MHz, 1602.5625 +/- 4MHz

GNSS Antenna L2 Band: 1227.6 +/- 1.023MHz

GNSS Antenna L5 Band: 1176 +/- 1.023MHz

Frequency (MHz)	L1: 1561-1602	L2: 1215-1237	L5: 1164-1189
Return Loss (dB)	< -10	< -10	< -10
Radiating Element Peak Gain (dBi/dBic)	>2.7/1.5	>1.7/0.2	>1/-2
Avg. Efficiency (%)	>60	>40	>40
LNA Gain (dB) Typical	28	33	30
Noise Figure (dB)	1.7 @1575MHz	2.2@1227MHz	2.2 @1164MHz
Operating Voltage ² (V)	2.5 - 18		
Power Consumption	Max. 16mA		

MECHANICAL SPECIFICATIONS

SKF5G72311DMLMR

SKF 7in1 antenna Dimension (Length x Width x Height)	Housing Material	Color	Weight	Fixing System	Mounting Hole Diameter
193.1 x 52.5 x 63.8 mm (7.62 x 2.07 x 2.51 inch)	PC, UV Protected	Black	550g (1.22lbs)	Direct Mount	1.063" (27mm)
Wireless Technology	No. of Port	Cable Length	Cable Type	Connector Type	
5G FR1/ LTE	2	17ft (5.181m)	LMR195	SMA (Male)	
WiFi 6E/7	3	17ft (5.181m)	LMR195	RP-SMA Male	
GNSS	1	17ft (5.181m)	RG-174	SMA (Male)	
UHF/VHF Whip	1	17ft (5.181m)	RG-174	SMA (Male)	

ENVIRONMENTAL SPECIFICATIONS

SKF5G72311DMWXXX

Operating Temperature	Storage Temperature	RoHS Compliant	Ingress Protection
-40 / +85° C	-40 / +85° C	Yes	IP67

Mechanical Drawing


SKF5G72311DMWXXX



Dimensions: inches (mm) Unless otherwise specified, all tolerances are ± 0.010 (0.25mm)

Mechanical Drawing

SKF5G72311DMW1585




Dimensions: inches (mm) Unless otherwise specified, all tolerances are ± 0.010 (0.25mm)

RF Test setup





SKF5G72311DMWXXX

- All measurements done on Ø 500mm (20") round ground plane.
- S-parameters with 5m LMR 195 cable
- Gain and Efficiency with 0.5m LMR 195 cable
- Measured at Pulse, Suzhou







Charts - VSWR, Isolation, Peak Gain, Efficiency

5G FR1





Radiation Pattern

5G FR1 Port 1



Radiation Pattern

5G FR1 Port 2





2230MHz
Avg(dBi) = -1.45
Peak(dBi) = 2.16
Avg -3(deg) = 58.5

3830MHz
Avg (dBi) = -3.97
Peak (dBi) = -0.12
Avg -3 (deg) = 144.5

800MHz
Avg (dBi) = -4.61
Peak (dBi) = 0.00
Avg -3 (deg) = 74.5

— 2230MHz — 3830MHz — 800MHz





2230MHz
Avg(dBi) = -2.55
Peak(dBi) = 2.98
Avg -3(deg) = 46.5

3830MHz
Avg (dBi) = -2.58
Peak (dBi) = 5.30
Avg -3 (deg) = 42.5

800MHz
Avg (dBi) = -3.52
Peak (dBi) = 1.49
Avg -3 (deg) = 50.5

— 2230MHz — 3830MHz — 800MHz





4710MHz
Avg(dBi) = -3.34
Peak(dBi) = 0.24
Avg -3(deg) = 135.5

5510MHz
Avg (dBi) = -4.96
Peak (dBi) = 0.00
Avg -3 (deg) = 62.5

6000MHz
Avg (dBi) = -7.87
Peak (dBi) = -3.44
Avg -3 (deg) = 76.5

— 4710MHz — 5510MHz — 6000MHz



4710MHz
Avg(dBi) = -1.08
Peak(dBi) = 4.63
Avg -3(deg) = 74.5

5510MHz
Avg (dBi) = -2.65
Peak (dBi) = 3.28
Avg -3 (deg) = 77.5


6000MHz
Avg (dBi) = -3.72
Peak (dBi) = 4.18
Avg -3 (deg) = 28.5

— 4710MHz — 5510MHz — 6000MHz


Charts - VSWR, Isolation, Peak Gain, Efficiency

WiFi 6E/7


VSWR vs Frequency
(WiFi 1,2,3) Measured on Ø0.5M (20") GP with 5m cable
Measured at Pulse, Suzhou - Dec 6 2020




Isolation vs Frequency
(WiFi 1,2,3) Measured on Ø0.5M (20") GP with 5m cable
Measured at Pulse, Suzhou - Dec 6, 2021



Peak Gain vs Frequency
(WiFi 1,2,3) Measured on Ø0.5M (20") GP with 500mm cable
Measured at Pulse, Suzhou - Dec 6 2021




Efficiency vs Frequency
(WiFi 1,2,3) Measured on Ø0.5M (20") GP with 500mm cable
Measured at Pulse, Suzhou - Dec 6 2021




Radiation Pattern


WiFi 6E/7 Port 1



WiFi 6E/7 Port 2





WiFi 6E/7 Port 3




Charts – VSWR

LMR Whip 150-160MHz











Frequency(MHz)	150	155	160
Peak Gain(dBi)	1.27	2.02	0.29











Charts – VSWR, Peak Gain, Efficiency

LMR Whip
380-430MHz










Charts – VSWR, Peak Gain, Efficiency

LMR Whip
450-512MHz




Charts – VSWR, Peak Gain, Efficiency

LMR Whip
740-960MHz




GNSS Antenna Return Loss

GNSS




GNSS Radiating Element Efficiency

GNSS




L1 Band



L2 + L5 Band


GNSS Radiating Element Peak Gain (Linear)



L1 Band


L2 + L5 Band

GNSS Antenna - LNA Gain




GNSS Antenna - LNA Out of band rejection

GNSS




GNSS Antenna - LNA Noise Figure

GNSS




L1 Noise Figure




L2 + L5 Noise Figure

GNSS Antenna - Radiation Patterns RHCP (dBic)

GNSS



L1 RHCP Pattern



L2 + L5 RHCP Pattern

Sharkfin / Vehicular

5G-FR1+WiFi-6E/7+GNSS L1+L2+LMR DM 7-in-1 Antenna

SKF5G72311DMWXXX - 617 to 7125 MHz + TETRA



PACKAGING

SKF5G72311DMWXXX

1pcs antennas per plastic bag

2pcs antennas per package box

Package box: 17x x12 x 9in

Notes:

1. Please contact sales for availability, lead time, and/or any special requests. Samples available upon request.

For More Information:

Americas - antennas.us@pulseelectronics.com | Europe – antennas.eu@pulseelectronics.com | Asia – antennas.as@pulseelectronics.com | Questions? +1-800-ANTENNA
Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright , 2023. Pulse Electronics, Inc. All rights reserved.
Company address: Pulse Electronics, a YAGEO Company, 15255 Innovation Drive, Suite #100, San Diego, CA 92128

'YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.'