



More Voltage & Power

Interconnect Solutions for Electrification





Table of Contents

About

Why High Voltage..... 3

Applications..... 4

Contacts 5

Contact Heat Rise Data..... 6

Connectors

Circular Connectors and Derivatives..... 7

High Voltage 38999 8

HV38999- How to Order 9

HV38999- How to Order- Receptacle..... 10

Bayonet Connectors..... 11

High Voltage 38999 SOLO 12

Megawatt Charging System..... 13

Voltarius..... 14

Voltarius Plug- How to Order 15


Voltarius Receptacle- How to Order..... 16

The world is gradually moving toward the electrification of everything. Consumer electric vehicles (EVs) have already made consistent progress toward mainstream adoption throughout the 2010s, while hybrid/electric military vehicles and electric vertical take-off and landing aircraft (eVTOL) are moving through development and inching toward common use. Homes, businesses, and buildings are seeing a rapid increase in the need for additional electric power, and the power grid is steadily being cycled off fossil fuels in favor of renewable energy.


These requirements will be especially apparent with eVTOL applications, for instance, which are slated to debut in major cities around the world this decade. eVTOLs are more power-hungry than their EV counterparts, with the nascent industry seeking batteries with double the standard energy density (450 watt-hours per kilogram). Meanwhile, the military is seeking an electric version of the Joint Light Tactical Vehicle (JLTV) — its 11-ton replacement of the Humvee that will have extensive power requirements of its own if adapted to an electric powertrain — and anticipates fielding fleets of electric vehicles in the future. Manufacturers require durable interconnect systems capable of handling these heavy power outputs.

From a technical perspective, to increase power output and meet growing industry goals, either the system voltage or current must be increased. Our contact technologies have been optimized over the years to raise current capacity while maintaining conductor size. However, until recently voltage requirements have remained relatively steady. Material and geometric enhancements have allowed us to safely expand the voltage capabilities of our connectors, even at altitude, while continuing to offer the robust use-life required for essential electrical systems. These improvements help to drive available power higher while avoiding significant increases in the weight and size of electrical systems.

In addition, design considerations have been made to accommodate power systems running at high frequencies and with large current excursions even at high operating temperatures. The potential of partial discharge has been mitigated through the use of sealing techniques as well as geometry enhancements to both insulators and conductors. Further improvements to discharge performance can be made through the full optimization of wire termination within the Amphenol family.



HIGH VOLTAGE 38999



TRADITIONAL 38999

Amphenol's selection of high-power and high-voltage connectors has been designed to meet the power demands of electric military vehicles, eVTOL aircraft, and that of an all-electric world head-on. We offer high-power and high-voltage connectors with our unique power-handling technologies based around a variety of specifications, including MIL-DTL-38999, MIL-DTL-5015, MGT-5015, and more.

APPLICATIONS



This collection of electric interconnects and contacts are designed for use in a variety of high-voltage and high-current applications, including:

- Hybrid/electric military vehicles
- Electric vertical takeoff and landing (eVTOL) aircraft
- Next-generation electric commercial aircraft, including business and regional jets
- Drones and UAVs
- Radar/surveillance systems
- Naval systems
- Laser power systems
- Spacecraft


SYSTEMS/COMPONENTS:

Energy storage, propulsion systems (primary power):

- Batteries
- Generators
- Power distribution units (PDU)
- Inverters
- Rectifiers
- Motors

Control surfaces, avionics, navigational equipment, environmental controls, in-flight entertainment (secondary power):

- Converters
- Inverters
- Actuators
- Power distribution units (PDU)





Amphenol offers a selection of contacts in a variety of sizes utilizing proprietary technologies to facilitate greater current carrying capacity and the ability to withstand the intense temperatures of high-amp applications. All power contacts leverage the high conductivity alloys and precision machining advancements incorporated initially in the Amphenol High Current Pin Contacts. These optimizations reduce power loss in your application and can improve ampacity by 15-25% through efficiency gains.

- Available with gold or silver plating
- Alternate termination types such as busbar and male/female threaded available for many connector types
- Optional touch proof tips provide an IP2X rating promoting operator safety for applicable connector series
- Crimp contacts optimized to accept an expanded range of wire diameters and types



RADSOK SOCKET CONTACT


RADSOK® contacts can handle up to 250 amps at size-0 contacts compared to 150 amps for size-0 mil-spec type standard sockets. RADSOK contacts also feature exceptionally high mating cycle durability and can withstand 20,000 mating cycles with standard silver plating. RADSOK contacts feature a geometric design that ensures a larger distribution of normal forces across the mating pin. These are ideal for high-amperage applications and are already available throughout the Amphenol product line for industrial, automotive, medical, and other industries.

- Highest current carrying capacity at lower temperatures, limited to 150C maximum temperature
- Maintains low insertion forces and high conductivity throughout its normal lifecycle

TEMPER-GRIP SOCKET CONTACT

Temper-Grip contacts, featuring low electrical resistance, are designed with harsh environments and high temperatures in mind. Temper-Grips can withstand up to 220 amps in a size-0 contact and are capable of operating in temperatures of more than 200 degrees Celsius. Temper-Grips take advantage of a “napkin-ring” design, first utilized in engine connectors, which prevents the copper tines from “relaxing” at higher temperatures, thus maintaining a greater conductive area in all situations.

- Highest current carrying capacity at higher operating temperatures
- Superior performance in high-vibration applications



Standard Contacts	
Size	Amps
16	13
12	23
8	46
4	80
0	150

High Performance Temper Grip Contacts	
Size	Amps
-	-
-	-
8	65
4	110
0	220

RADSOK Contacts	
Size	Amps
-	-
-	-
8	70
4	120
0	250






CONTACT HEAT RISE DATA





The data below shows expected heat rise for High Performance Temper Grip Contacts (sizes 0, 4, & 8) and for High Performance Contacts (sizes 12 & 16) compared to an ideal case, uncut wire (wire gauge matches contact size). The Standard Contacts meet mil-spec requirements but lack optimizations to reduce resistance and thus heat rise. Data is provided for designer justification to operate beyond the typical 40C heat rise limits where appropriate.

HIGH PERFORMANCE TEMPER GRIP CONTACTS




HIGH PERFORMANCE CONTACTS



Test data collected using bare contact mated pairs in still, room temperature air. Current applied until contacts reached thermal stability. Data shown is not de-rated. Testing recommend in actual application to account for cooling effects, current excursions, contact wear, etc. Note that the establishment of electrical safety factors is left entirely up to the system designer, as they are in the best position to know what characteristics can be expected in a particular system.





The collection of power connectors was designed to improve and expand upon the electrical performance of existing mil-spec type connectors. Utilizing our advanced insert and contact technologies, we are able to increase the operating voltages at altitude as well as operating currents while maintaining the robust environmental and mechanical performance already offered in our qualified military specification shells.

- Utilizing familiar military specification shell types, materials, and finishes
- Compatible with high performance contacts detailed on pages 5 & 6








CUSTOM DERIVATIVES IN DEVELOPMENT:

- Manual Service Disconnect (MSD) - Three stage plug for system maintenance
- Bulkhead Feedthrough - Receptacle installed between sealed/unsealed areas accepting plugs on both sides
- Rack and Panel - Blind mate connection with float mount functionality (below left)
- Dualok® - Vibration resistant plug prevents unintended disengagement during operation (below right)
- PCB Mount - Contacts with tails for soldering and shells available with threaded PCB mounting points
- Feedthrough - Customizable connector style with bolted termination, and optimized size/ weight for electrical performance (above right)



Shell Size & Insert Arrg.:	13-54		15-54		15-58		17-58		17-59		19-59		21-56		23-59	
Number of Contacts	4	0	2	2	4	4	4	4	1	2	1	2	2	4	1	2
Contact Size	16	22D	16	12	16	22D	12	22D	8	22D	4	22D	8	22D	0	22D




Shell Size & Insert Arrg.:	25-56		25-58		33-58		37-56		37-57	
Number of Contacts	2	4	4	4	4	4	2	4	3	4
Contact Size	4	22D	8	22D	4	22D	0	22D	0	22D

**Some insert arrangements may have extended initial lead time depending on tool status.
Please consult factory for more information.



CONTACT LEGEND 0 4 8 12 16 22D



High Voltage 38999 (HV38999) is an expansion of MIL-DTL-38999 type connectors developed to provide solutions for next generation power requirements.

Future power distribution architecture is moving toward higher voltages beyond the capabilities of standard connectors. Through insert optimizations these specialty D38999s can safely carry high voltages and large currents while remaining partial discharge free to extend connector life.

FEATURES & BENEFITS:

- Designed to meet MIL-DTL-38999 mechanical and environmental performance
- Available safety interlock circuitry utilizes last mate, first break sequence
- All MIL-DTL-38999 shell configurations/finishes available including our Dualok high vibration plug
- Utilizes existing AS39029 type silver plated power contacts including the higher current Temper Grip socket and busbar/threaded termination styles.
- Accommodates standard MIL-DTL-38999 accessories

Test Voltages (Pre-Production Arrangement 13-54)*				
ALTITUDE	DWV Test Voltages A/C (RMS)		PDIV Test Voltages A/C (RMS)	PDIV Test Voltage D/C
	Unmated	Mated		
SEA LEVEL	2600V	4500V	1550V	2000V
20,000 FT	N/A	3850V	1250V	1700V
30,000 FT		3700V	1100V	1400V
50,000 FT		3000V	850V	1150V

*13-54 arrangement excepted to be lowest rated arrangement. Electrical data for other arrangements available soon

**Note that the establishment of electrical safety factors is left entirely up to the system designer as they are in the best position to know what peak voltage, switching surges, transients, etc. can be expected in a particular system

1.	2.	3.	4.	5.	6.	7.
Connector Type	Shell Style	Service Class	Shell Size - Insert Arrangement	Crimp Termination	Alternate Positions	Modifications
HV	97	DZ	25-56	GH		(RDG)
HV	06	RF	13-54	P	A	

1. Connector Type

HV	High Voltage 38999
HVC	High Voltage Composite 38999***

4. Shell Size - Insert Arrangement**

Shell Size & Insert Arrangements on page 7

5. Crimp Termination

Add "G" before contact type designation for gold plated contacts

P	Pin Contacts
S	Socket Contacts
A	Pin, Less Contacts
B	Socket, Less Contacts
H	High Performance Temper Grip Socket
R	RADSOK Socket

2. Shell Style**

00	Wall Mount Receptacle
01	Inline Receptacle
02	Box Mount Receptacle
06	Straight Plug
56	DUALOK Plug
96	Plug with Integral Backshell
07	Jam Nut Receptacle
97	Reduced Flange Jam Nut Receptacle

6. Alternate Positions






	Blank for normal rotation
A	A rotation
B	B rotation
C	C rotation
D	D rotation
E	E rotation

7. Modifications**

P3D = 3D Printed, recommended for fit checks and benchtop testing

(3D1)	P3D Metal Clip Insert, Standard Shell
(TPS)	Touch Proof Tips (Pin contacts only)
(RDG)	Reduced Grommet*

3. 175°C Service Class


RW	Olive Drab Cadmium Plated Aluminum (500 Hour Salt Spray) or Composite (2000 Hour Salt Spray)	
DT	Durmalon Plated Aluminum (500 Hour Salt Spray)	
DZ	Black Zinc-Nickel Plated Aluminum (500 Hour Salt Spray)	
RF	Electroless Nickel Plated Aluminum (48 Hour Salt Spray) or Composite (2000 Hour Salt Spray)	
RK	Passivated Stainless Steel, Firewall (500 Hour Salt Spray) ****	
RKN	Passivated Stainless Steel, Non-Firewall (500 Hour Salt Spray)	
RL	Nickel Plated, Passivated Stainless Steel, Non-Firewall (500 Hour Salt Spray)	
RS	Nickel Plated, Passivated Stainless Steel, Firewall (500 Hour Salt Spray) ****	
DS	AP-93 Tri-Nickel Alloy Plated Aluminum (1000 Hour Salt Spray)	

*Provides compatibility for size 0 contacts with 2awg, size 4 contacts with 6awg, and size 8 contacts with 10awg. Crimp well reducer bushings are included.

**Contact factory for additional configurations/customization

***Available for insert arrangements 13-54, 15-54, 15-58 and 17-58

**** Contact factory for firewall performance



HV38999 HOW TO ORDER- ALTERNATE RECEPTACLE TERMINATION



1.	2.	3.	4.	5.	6.	7.	8.
Connector Type	Shell Style	Service Class	Shell Size - Insert Arrangement	Contact Style	Contact Type	Alternate Positions	Modifications
HV	02	RF	25-56	F	P	A	(MTT)
HV	27	RW	37-57	B	R		

1. Connector Type

HV High Voltage 38999

4. Shell Size - Insert Arrangement**

Shell Size & Insert Arrangements on page 7

5. Contact Style**

F Female Thread Termination
M Male Thread Termination
B Busbar

8. Modifications**

P3D = 3D Printed, recommended for fit checks and benchtop testing

(3D1) P3D Metal Clip Insert, Standard Shell
(TPS) Touch Proof Tips (Pin contacts only)
(MTT) Termination With Metric Threading

2. Shell Style**

02 Box Mount Receptacle
27 Jam Nut Box Mount
97 Reduced Flange Jam Nut Receptacle

6. Contact Type

Add "G" before contact type designation for gold plated contacts

P Pin Contacts
S Socket Contacts
H High Performance Temper Grip Socket
R RADSOK Socket

7. Alternate Positions

Blank for normal rotation
A A rotation
B B rotation
C C rotation
D D rotation
E E rotation

3. 175°C Service Class

RW Olive Drab Cadmium Plated Aluminum (500 Hour Salt Spray)
DT Duralon Plated Aluminum (500 Hour Salt Spray)
DZ Black Zinc-Nickel Plated Aluminum (500 Hour Salt Spray)
RF Electroless Nickel Plated Aluminum (48 Hour Salt Spray)
RK Passivated Stainless Steel, Firewall (500 Hour Salt Spray) ***
RKN Passivated Stainless Steel, Non-Firewall (500 Hour Salt Spray)
RL Nickel Plated, Passivated Stainless Steel, Non-Firewall (500 Hour Salt Spray)
RS Nickel Plated, Passivated Stainless Steel, Firewall (500 Hour Salt Spray)***
DS AP-93 Tri-Nickel Alloy Plated Aluminum (1000 Hour Salt Spray)



**Contact factory for additional configurations/customization

***Contact factory for firewall performance

Termination Thread Size*

Contact Size	Imperial	Metric
8	4-40 UNC	M3 x 0.5
4	8-32 UNC	M4 x 0.7
1/0	10-32 UNF	M5 x 0.8

*Default thread type is imperial. Use (MTT) mod code for metric



QUICK-LOK

The QUICK-LOK product line is a descendant of the HV38999 product profile which is designed to provide solutions for next generation power requirements. QUICK-LOK offers a bayonet coupling mechanism which allows for quick, ¼ turn mating, with confirmation of a full mate via an audible indication when the bayonet pins lock into position.



HVGT

The HVGT connector series, with reverse bayonet coupling, packages the high voltage/power HV38999 inserts into a ruggedized shell with roots in the military market. The insert technology allows for higher power density per shell when compared to traditional MIL-DTL-5015 arrangements. Extended creepage paths for high voltage operation may also provide a larger safety factor in environments with a high degree of pollution.



FEATURES & BENEFITS:

- Audible and tactile feedback when fully mated
- Assurance of fully mated connectors in visually restricted areas
- Available safety interlock circuitry utilizes last mate, first break sequence
- Designed to meet applicable mechanical and environment requirements for aircraft and military ground vehicles


HV38999 Test Voltages (Pre-Production Arrangement 13-54)*				
ALTITUDE	DWV Test Voltages A/C (RMS)		PDIV Test Voltages A/C (RMS)	PDIV Test Voltage D/C
	Unmated	Mated		
SEA LEVEL	2600V	4500V	1550V	2000V
20,000 FT	N/A	3850V	1250V	1700V
30,000 FT		3700V	1100V	1400V
50,000 FT		3000V	850V	1150V

*13-54 arrangement excepted to be lowest rated arrangement. Electrical data for other arrangements available soon

**Note that the establishment of electrical safety factors is left entirely up to the system designer as they are in the best position to know what peak voltage, switching surges, transients, etc. can be expected in a particular system




Space Saving Single Pole Form Factor




HV38999 SOLO is a sibling product of the HV38999 Product Series. This adaption prioritizes weight and size in a single pole form factor while maintaining insert optimizations for high voltage and power.

- Designed to meet MIL-DTL-38999 mechanical and environmental performance
- All MIL-DTL-38999 shell materials/finishes available including composites and our high vibration Dualok plug
- Accommodates contact sizes 8, 4, and 0 from page 5 & 6
- Product series includes shield termination backshell reducing the required part numbers
- Provides robust environmental performance for large cables with integral dynamic o-ring sealing



Shell Size & Insert Arrg.:	11-51	13-51	17-51
Number of Contacts	1	1	1
Contact Size	8	4	0

For Next Generation Vehicle Charging Requirements



The Megawatt Charging System (MCS) is an interconnect system defined by electrification industry leaders designed to deliver the high voltages and powers from ground infrastructure to energy storage systems in electric/hybrid aircraft and ground vehicles.

- Ruggedized MCS inlet for aerospace/military applications will coincide with a future SAE specification
- Ground charging plug and cable assembly designed and built by the Amphenol Industrial Group


THREE LEVELS OF ELECTRICAL PERFORMANCE:

- Level I: 1250Vdc, 350A
- Level II: 1250Vdc, 1000A (cooled plug)
- Level III: 1250Vdc, 3000A (cooled plug and inlet)

INLET CONNECTOR KEY FEATURES:

- Communication and interlock functionality via dedicated contacts
- Programmable LEDs for charging status
- Integral actuator to prevent disengagement during charging
- Flexible main pole termination solutions
- Utilizes specialized Amphenol technology to increase inlet mating cycles up to 100X compared to mil-spec connectors

Ruggedized High Power Interconnect



Voltarius is a high voltage, latch assisted connector based off the Amphenol Industrial Powerlok connector with upgrades to enhance performance for military and aerospace applications. These aluminum connectors are optimized for larger conductor sizes in single, double, and triple pole configurations while maintaining essential safety features such as touch proof contacts and interlock circuitry.

KEY FEATURES

- Receptacle can be configured as a drop-in replacement for the Powerlok G2 connector
- Design mitigates partial discharge for operation with high voltages at altitude (1000V at 30,000 ft expected)
- 250A or 450A rated contacts provisioned for 4AWG to 4/0AWG wiring (see page 6 for derating)
- Designed to meet applicable mechanical and environmental requirements for aircraft and military vehicles
- Metal latch with secondary locking ensures rigid shell to shell bottoming
- 6 contact pass-through last mate, first break safety interlock circuitry integral to design (multi-pole only)
- Independent shield termination provisions for interlocks and power poles
- Dust caps and strain relief hardware available

VOLTARIUS PLUG- HOW TO ORDER



1.	2.	3.	4.	5.	6.	7.	8.	9.	10.
Connector Type	Shell Style	Service Class	Number of Poles	Shell/Contact Size	Sealing Range/Crimp Well Size	Contact Type	Alternate Rotations	Interlocks	Mod Code
VT	06	DZ	2-	3	ED-	H	N	L	(CAP)

1. Connector Type

VT	Voltarius
-----------	-----------

2. Shell Style

06	Straight Plug
-----------	---------------

3. Service Class

DW	Olive Drab Cadmium Plated Aluminum (500 Hour Salt Spray)	
DT	Duralon Plated Aluminum (500 Hour Salt Spray)	
DZ	Black Zinc-Nickel Plated Aluminum (500 Hour Salt Spray)	
DR	Electroless Nickel Plated Aluminum (48 Hour Salt Spray)	
DS	AP-93 Tri-Nickel Alloy Plated Aluminum (1000 Hour Salt Spray)	

4. Poles

1-	Single**
2-	Double
3-	Triple

5. Cable Size

306	6 awg
304	4 awg
302	2 awg
301	1 awg
310	1/0 awg
320	2/0 awg

6. Sealing Range/Crimp Well Size

4 awg to 4/0 awg available. Contact factory for sealing ranges and crimp well options

7. Contact Type

H	High Performance Temper Grip Socket
R	RADSOK Socket

8. Alternate Rotations

N	Normal Rotation*
A	A Rotation
B	B Rotation
C	C Rotation
D	D Rotation
E	E Rotation

*For multi-pole configurations use "N" (user configurable rotations)

9. Interlocks

P	Pin Interlocks**
N	Less Interlocks

**Single pole currently only available less interlocks. Multi-pole includes 6 interlocks per module

10. Mod Code

(CAP)	Protective Dust Cap
--------------	---------------------



VOLTARIUS RECEPTACLE- HOW TO ORDER



1.	2.	3.	4.	5.	6.	7.	8.	9.	10.	11.
Connector Type	Shell Style	Service Class	Number of Poles	Shell/Contact Size	Contact Termination	Termination Size	Contact Type	Alternate Rotations	Interlocks	Mod Code
VT	02	DZ	2-	3	Z	1-	P	N	L	(CAP)

1. Connector Type

VT	Voltarius
-----------	-----------

2. Shell Style

02	Flange Mount Receptacle
-----------	-------------------------

3. Service Class

DW	Olive Drab Cadmium Plated Aluminum (500 Hour Salt Spray)	
DT	Durmalon Plated Aluminum (500 Hour Salt Spray)	
DZ	Black Zinc-Nickel Plated Aluminum (500 Hour Salt Spray)	
DR	Electroless Nickel Plated Aluminum (48 Hour Salt Spray)	
DS	AP-93 Tri-Nickel Alloy Plated Aluminum (1000 Hour Salt Spray)	

4. Poles

1-	Single**
2-	Double
3-	Triple

5. Shell/Contact Size

3	250A Rated Contact
5	450A Rated Contact

6. Contact Termination

Z	Through-hole
T	Threaded Busbar
F	Female Threaded Termination
M	Male Thread Termination

7. Termination Size

See table 3 for Termination Sizes

8. Contact Type

P	Pin
----------	-----

9. Alternate Rotations

N	Normal Rotation*
A	A Rotation
B	B Rotation
C	C Rotation
D	D Rotation
E	E Rotation

10. Interlocks

S	Socket Interlocks**
N	Less Interlocks

**Single pole currently only available less interlocks. Multi-pole includes 6 interlocks per module

11. Mod Code

(CAP)	Protective Dust Cap
--------------	---------------------

*For multi-pole configurations use "N" (user configurable rotations)



Table 3 - Termination Size

Designator	Thread Type			
	Through-Hole Busbar	Threaded Busbar	Female Threaded Termination	Male Threaded Termination
1	6.5 mm	M6X1-7H	TBD	TBD
B	0.265 in	.250-20UNC		

**Amphenol Aerospace Operations**

40-60 Delaware Avenue
Sidney, NY 13838
800-678-0141

Amphenol Commercial Air Division

40-60 Delaware Avenue
Sidney, NY 13838
1-800-687-0141

Amphenol Nexus Technologies

316 Courtland Avenue
Stamford, CT 06906
203-327-7300

Amphenol PCD

72 Cherry Hill Drive
Beverly, MA 01915
978-624-3400

Amphenol SV Microwave

2400 Centrepark West Drive
West Palm Beach, FL
561-840-1800

Amphenol Times Microwave, Inc.

358 Hall Avenue
Wallingford, CT 06492
800-867-2629

Amphenol Fiber Systems**International**

1300 Central Expressway North, Suite
100
Allen, TX 75013
214-547-2400

Amphenol Borisch Technologies

4511 East Paris Avenue
Grand Rapids, MI 49512
616-554-9820

Amphenol Printed Circuits

91 Northeastern Boulevard
Nashua, NH 03062
603-324-4500

Amphenol Canada

5950 14th Ave
Markham, ON L3S 3K5
416-291-4401

Amphenol XMA

7 Perimeter Road
Manchester, NH 03103
603-222-2256

Amphenol Q Microwave

1591 Pioneer Way
El Cajon, CA 92020
619-258-7322

Amphenol CIT

100 Tensolite Dr.
St. Augustine, FL 32092
800-458-9960

Amphenol Invotec

Unit 1-3, Hedging Lane Industrial Estate
Dosthill, Tamworth, B77 5HH United
Kingdom
+44 (0) 1827 263250

Amphenol Ionix Systems

Prospect House, Taylor Business Park
Risley, Warrington, WA3 6HP United
Kingdom
+44 (0) 1942 685200

Amphenol Limited

Thanet Way
Whitstable, Kent, CT5 3JF United Kingdom
+44 (0) 1227 773200

Amphenol Socapex

948 Promenade De L'Arve – BP 29
74311 Thyez France
+33 (0) 4 50 89 28 00

Amphenol Air LB SAS

2 Rue Clément Ader, Zac de Wé
08110 Carignan France
+33 (0) 03 24 22 78 49

Amphenol AirLB GmbH

Am Kleinbahnhof 4
D-66740 Saarlouis Germany
+49 (0) 68 31/98 10 0

Amphenol SEFEE

Z.I. des Cazes – BP243
12402 Saint-Affrique Cedex
France
+33 (0) 5 65 98 11 00

Amphenol Interconnect India

105, Bhosari Industrial Area
Pune – 411 026 India
+91 20 27120363

Amphenol Japan, Ltd.

471-1, Deba, Ritto-City
Shiga, 520 3041 Japan
+81 77 553 8501

Amphenol Martec Limited

St. Augustines Business Park
Swalecliffe, Whitstable, Kent
CT5 2QJ United Kingdom
+44 (0) 1227 793 733

Amphenol Optimize

Carretera Internacional Km 6.5
Col. Parque Industrial
Nogales, Sonora, México. C.P.
84094
+52 (631) 311-160

Amphenol Ionix Systems OÜ

Pikk Street 59b
Kuressaare 93815 Estonia
+372 4521 780

AMAO – European Sales**Operations**

Via Barbaiana 5
20020 Lainate Milano, Italy
+39 02 932 541

Amphenol Bar-Tec Ltd.

3 Hagavish st
POB 2479 Kfar-Saba 44641
Israel +972-9-7644100

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind expressed or implied. Statements or suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should not assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

Notes

[illegible]

[illegible]



AMPHENOL CORPORATION

40-60 Delaware Avenue, Sidney, NY 13838-1395 • 800-678-0141
www.amphenol-aerospace.com • www.amphenolmao.com