

# Single-chip Type with Built-in FET Switching Regulator Series





# Simple Step-down Switching Regulators with Built-in Power MOSFET

BD9701FP/CP-V5/T/T-V5, BD9703FP/CP-V5/T/T-V5,BD9702CP-V5/T/T-V5

No.09027EBT01

#### Description

The BD9701/BD9703/BD9702 are single-channel step-down switching regulator capable of PWM operation. The Pch MOS FET is built in for high efficiency in small load area. Lower electricity consumption of operating current 4mA (Typ) and stand-by current 0uA(Typ) is realized by adopting Bi-CMOS process.

#### Features

- 1) Maximum switching current: 1.5A(BD9701/BD9703), 3A(BD9702)
- 2) Built-in Pch FET ensures high efficiency
- 3) Output voltage adjustable via external resistors
- 4) High switching frequency: 100kHz (BD9701), 300kHz(BD9703), 110kHz(BD9702)
- 5) Overcurrent and thermal shutdown protection circuits built in
- 6) ON/OFF control via STBY pin
- 7) Small surface mount TO252-5 package (only BD9701FP, BD9703FP)

#### Applications

TVs, printers, DVD players, projectors, gaming devices, PCs, car audio/navigation systems, ETCs, communication equipment, AV products, office equipment, industrial devices, and more.

#### ●Line Up

	BD9701FP/CP-V5/T/T-V5	BD9703FP/CP-V5/T/T-V5	BD9702CP-V5/T/T-V5		
Output Current	1.5A		3.0A		
Input Voltage		8 or Vo+3 ~	36V		
Switching Frequency	100kHz (fixed)	300kHz (fixed)	110kHz (fixed)		
External Synchronization	×				
Stand-by Function	0				
Operating Temperature	-40 ∼ +85°C				
Package	TO252-5/TO220CP-V5/T0	O220FP-5/TO220FP-5 (V5)	TO220CP-V5/TO220FP-5/TO220FP-5 (V5)		

● Absolute Maximum Ratings (Ta=25°C)

Paramete	er	Symbol	Ratings	Unit
Supply Voltage (V	(CC-GND)	VCC	36	V
STBY-GN	ID	V <sub>STBY</sub>	36	V
OUT-GN	D	Vo	36	V
INV-GNI	)	V <sub>INV</sub>	10	V
Maximum Switching Current	BD9701/BD9703	laut	1.5	_
	BD9702	lout	3	A
Power Dissipation TO252		D.I.	0.8 (*1)	101
'	TO220	Pd	2 <sup>(*2)</sup>	W
Operating Temp	perature	Topr	-40~+85	°C
Storage Tempo	erature	Tstg	-55~+150	°C

<sup>\*1</sup> Without external heat sink, the power dissipation reduces by 6.4mW/°C over 25°C.

Troubled by Toom To 9, Whom Thousand on Thinney 6125 Houlding

# ●Operating Conditions(Ta=-40~+85°C)

Dorometer	Cymbol	Limit				
Parameter	Symbol	MIN	TYP	MAX	Unit	
Input Voltage	VCC	8.0 or Vo+3 <sup>(*3)</sup>	-	35.0	V	
Output Voltage	Vo	1.0	-	32	V	

<sup>\*3</sup>The minimum value of an input voltage is the higher either 8.0V or Vo+3

#### Electrical Characteristics

OBD9701FP/CP-V5/T/T-V5 (Unless otherwise noted, Ta=25°C,VCC=12V,Vo=5V,STBY=3V)

Parameter		Symbol	Limit			Unit	Conditions
		Symbol	MIN	TYP	MAX	Offic	Conditions
Output ON Resistance		Ron	-	1.0	1.5	Ω	design guarantee
Efficiency		η	-	86	-	%	Io=0.5A design guarantee
Switching Frequency		fosc	80	100	120	kHz	
Load Regulation		ΔVOLOAD	-	10	40	mV	VCC=20V,lo=0.5~1.5A
Line Regulation		ΔVOLINE	-	40	100	mV	VCC=10~30V,Io=1.0A
Over Current Protection Limit		locp	1.6	-	-	Α	
INV Pin Threshold Voltage	INV Pin Threshold Voltage		0.98	1.00	1.02	V	
INV Pin Threshold Voltage Thermal Variation	INV Pin Threshold Voltage Thermal Variation		-	±0.5	-	%	Tj=0∼85°C design guarantee
INV Pin Input Current	INV Pin Input Current		-	1	-	μA	VINV=1.0V
STBY Pin	ON	VSTBYON	2.0	-	36	V	
Threshold Voltage	OFF	VSTBYOFF	-0.3	-	0.3	V	
STBY Pin Input Current		Istby	5	25	50	μΑ	STBY=3V
Circuit Current		Icc	-	4	12	mA	
Stand-by Current		Ist	-	0	5	μΑ	STBY=0V

This product is not designed to be resistant to radiation.

<sup>\*2</sup> Without external heat sink, the power dissipation reduces by 16.0mW/°C over 25°C. Reduced by 160mW/°C, when mounted on Infinity size heatsink.

# Electrical Characteristics

OBD9703FP/CP-V5/T/T-V5 (Unless otherwise noted, Ta=25°C,VCC=12V,Vo=5V,STBY=3V)


Parameter		Symbol	Limit			Unit	Conditions
		Symbol	MIN	TYP	MAX	Onit	Conditions
Output ON Resistance		Ron	-	1.0	1.5	Ω	design guarantee
Efficiency		η	-	86	-	%	Io=0.5A design guarantee
Switching Frequency		fosc	270	300	330	kHz	
Load Regulation		ΔVOLOAD	-	10	40	mV	VCC=20V,Io=0.5~1.5A
Line Regulation		ΔVOLINE	-	40	100	mV	VCC=10~30V,lo=1.0A
Over Current Protection Limit		Іоср	1.6	-	-	Α	
INV Pin Threshold Voltage		VINV	0.98	1.00	1.02	V	
INV Pin Threshold Voltage Thermal Variation		ΔVΙΝV	-	±0.5	-	%	Tj=0∼85°C design guarantee
INV Pin Input Current	INV Pin Input Current		-	1	-	μΑ	VINV=1.0V
STBY Pin	ON	VSTBYON	2.0	-	36	V	
Threshold Voltage	OFF	VSTBYOFF	-0.3	-	0.3	V	
STBY Pin Input Current		Istby	5	25	50	μΑ	STBY=3V
Circuit Current		Icc	-	5	12	mA	
Stand-by Current		Ist	-	0	5	μA	STBY=0V

# Electrical Characteristics


OBD9702FP/CP-V5/T/T-V5 (Unless otherwise noted, Ta=25°C,VCC=12V,Vo=5V,STBY=3V)

Parameter		Cymbol	Limit			Unit	Conditions
		Symbol	MIN	TYP	MAX	Offic	Conditions
Output ON Resistance		Ron	-	0.5	1.5	Ω	design guarantee
Efficiency		η	-	86	-	%	Io=1A design guarantee
Switching Frequency		fosc	88	110	132	kHz	
Load Regulation		ΔVOLOAD	-	10	40	mV	VCC=20V,Io=1~3A
Line Regulation		ΔVOLINE	-	40	100	mV	VCC=10~30V,Io=1.0A
Over Current Protection Limit		locp	3.2	-	-	Α	
INV Pin Threshold Voltage		VINV	0.98	1.00	1.02	V	
INV Pin Threshold Voltage Thermal Variation		ΔVΙΝV	1	±0.5	-	%	Tj=0∼85°C design guarantee
INV Pin Input Current		IINV	-	1	-	μA	VINV=1.0V
STBY Pin	ON	VSTBYON	2.0	-	36	V	
Threshold Voltage	OFF	VSTBYOFF	-0.3	-	0.3	V	
STBY Pin Input Current		Istby	5	25	50	μΑ	STBY=3V
Circuit Current		Icc	-	4	12	mA	
Stand-by Current		Ist	-	0	5	μA	STBY=0V

# ●Characteristic Data OBD9701FP/CP-V5/T/T-V5



●Characteristic Data
OBD9702FP/CP-V5/T/T-V5








Fig.19 EFFICIENCY-LOAD CURRENT




Fig.20 OCP VCC=20V




Fig.21 fosc-Ta




Fig.22 OUTPUT VOLTAGE-LOAD CURRENT




Fig.23 OUTPUT VOLTAGE-INPUT VOLTAGE (Vo=5V,Ro=5ohm)




Fig.24
CIRCUIT CURRENT-INPUT
VOLTAGE NO LOAD




Fig.25
VOUT~OUT
VOLTAGE-DRAIN CURRENT




Fig.26 fosc-INPUT VOLTAGE





Fig.27
INV THRESHOLD VOLTAGE-Ta


# ●Block Diagram

BD9701FP/CP-V5/T/T-V5, BD9703FP/CP-V5/T-V5, BD9702CP-V5/T/T-V5

# TO252-5 Package Dimensions (mm)



# **TO220CP-V5 Package Dimensions (mm)**







Fig.28 Block Diagram

#### ●Pin Description


Pin No.	Pin Name	Function
1	VCC	Input Power Supply Pin
2	OUT	Internal Pch FET Drain Pin
3,FIN(*2)	GND	Ground
4	INV	Output Voltage Feedback Pin
5	STBY	ON/OFF Control Pin

(\*2)FIN is assigned in the case of TO252-5.

# **TO220FP-5 Package Dimensions (mm)**



# TO220FP-5(V5) Package Dimensions (mm)



#### Block Function Explanations

VREF

Generates the regulated voltage from VCC input, compensated for temperature.

#### OSC

Generates the triangular wave oscillation frequency using an internal resistors and capacitor. Used for PWM comparator input.

#### Error AMP

This block, via the INV pin, detects the resistor-divided output voltage, compares this with the reference voltage, then amplifies and outputs the difference.

#### PWM COMP

Outputs PWM signals to the Driver block, which converts the error amp output voltage to PWM form.

#### DRIVER

This push-pull FET driver powers the internal Pch MOSFET, which accepts direct PWM input.

#### STBY

Controls ON/OFF operation via the STBY pin. The output is ON when STBY is High.

#### Thermal Shutdown (TSD)

This circuit protects the IC against thermal runaway and damage due to excessive heat. A thermal sensor detects the junction temperature and switches the output OFF once the temperature exceeds a threshold value (175deg). Hysteresis is built in (15deg) in order to prevent malfunctions due to temperature fluctuations.

### Over Current Protection (OCP)

The OCP circuit detects the voltage difference between VCC and OUT by measuring the current through the internal Pch MOSFET and switches the output OFF once the voltage reaches the threshold value. The OCP block is a self-recovery type (not latch).

#### Timing Chart





Fig.29 Timing Chart

#### Notes for PCB layout



- Place capacitors between VCC and Ground, and the Schottky diode as close as possible to the IC to reduce noise and maximize efficiency.
- Connect resistors between INV and Ground, and the output capacitor filter at the same Ground potential in order to stabilize the output voltage.
- Application component selection and settings

#### Inductor L1

If the winding resistance of the choke coil is too high, the efficiency may deteriorate.

As the overcurrent protection operates over minimum 1.6A (BD9701FP/CP-V5/T/T-V5, BD9703FP/CP-V5/T-V5) or 3.2A minimum (BD9701CP-V5/T/T-V5), attention must be paid to the heating of the inductor due to overload of short-circulated load

Note that the current rating for the coil should be higher than  $I_{OUT}(MAX) + \angle IL$ . lout (MAX): maximum load current If you flow more than maximum current rating, coil will become overload, and cause magnetic saturation, and those account for efficiency deterioration. Select from enough current rating of coil which doesn't over peak current.

$$\triangle IL_{\perp} = \frac{(VCC-VOUT)}{L1} \times \frac{VOUT}{VCC} \times \frac{1}{fosc}$$

L1:inductor value, VCC:maximum input voltage, VOUT:output voltage, ⊿IL:coil ripple current value, fosc:oscillation frequency

#### Shottky Barrier Diodes D1

A Schottky diode with extremely low forward voltage should be used. Selection should be based on the following guidelines regarding maximum forward current, reverse voltage, and power dissipation:

- The maximum current rating is higher than the combined maximum load current and coil ripple current ( $\Delta I_1$ ).
- The reverse voltage rating is higher than the VIN value.
- Power dissipation for the selected diode must be within the rated level.

The power dissipation of the diode is expressed by the following formula:

Pdi=lout(MAX)×Vf×(1-VOUT/VCC)

lout (MAX): maximum load current, Vf: forward voltage, VOUT: output voltage, VCC: input voltage

#### Capacitor C1,C2,C3,C4,C5

As large ripple currents flow across C1 and C3 capacitors, high frequency and low impedance capacitor for a switching regulator must be used. The ceramic capacitor C2 must be connected. If not, noise may cause an abnormal operation. If the ripple voltage of input and output is large, C4 selected among ceramic, tantalum and OS capacitor with low ESR may decrease the ripple, however if the only low ESR capacitor is used, an oscillation or unstable operation may be caused. C5 is the capacitor for phase compensation and normally not used. If you need to improve the stability of feedback network, connect C5 between INV and OUTPUT.

#### Feed back resistance R1,R2

The offset of output voltage is determined by both Feed back resistance and INV pin input current.

VOUT=(R1+R2) VINV/R2 (VINV pin Threshold Votage)

If Feed back resistance is high, the setting of output voltage will be move.

Recommended : Resistance between INV pin and GND = less than  $10k\Omega$ .

#### Recommended Circuit




Fig.31 Recommended Circuit Output Voltage 5V: Application cicuit example

#### (BD9701FP/CP-V5/T/T-V5)

<Recommended Components (Example)>

Capacitor C1= $100\mu F(50V)$  :Al electric capacitor UHD1H101MPT (nichicon)

C2=OPEN

C3=220µF(25V) :Al electric capacitor UHD1E221MPT (nichicon)

C4=OPEN C5=OPEN

< Recommended Components example 2>

Capacitor C1=220μF(25V) :Al electric capacitor UVR1H221MPA (nichicon)

C2=1.0μF(50V) :ceramic cap UMK212F105ZG (TAIYO YUDEN)
C3=470μF(16V) :AI electric capacitor UVR1E471MPA (nichicon)

C4=150µF(20V) :OS capacitor 20SVP150M (SANYO)

C3=OPEN :OS capacitor 205 VP 150 M (SAN Y

#### (BD9703FP/CP-V5/T/T-V5)

#### <Recommended Components>

:CDRH127/LD (sumida) Inductor  $L1=47\mu H$ Schotky Diode D1 :RB050LA-40 (ROHM)

Capacitor  $C1 = 100 \mu F(50 V)$ :Al electric capacitor UHD1H101MPT (nichicon)

> $C2=2.2\mu F(50V)$ :ceramic cap CM43X7R225K50A (KYOCERA)  $C3 = 470 \mu F(25V)$ :Al electric capacitor UHD1E471MPT (nichicon)

C4=OPEN

C3=OPEN

#### (BD9702CP-V5/T/T-V5)

#### < Recommended Components >

Inductor  $L1=47\mu H$ :CDRH127/LD (sumida) Schotky Diode D1 :RB050LA-40 (ROHM)

Capacitor  $C1 = 1000 \mu F(50V)$ :Al electric capacitor UHD1H102MPT (nichicon)

C2=OPEN

 $C3 = 1000 \mu F(25V)$ :Al electric capacitor UHD1E102MPT (nichicon)

C4=OPEN C3=OPEN

## ●Test Circuit




Fig.32 Input Output Measurement Circuit

#### ●I/O Equivalent Circuit




Fig.33Input Output Equivalent Circuit

#### Notes for use

#### 1. Absolute Maximum Ratings

Use of the IC in excess of absolute maximum ratings such as the applied voltage or operating temperature range may result in IC deterioration or damage. Assumptions should not be made regarding the state of the IC (short mode or open mode) when such damage is suffered. A physical safety measure such as a fuse should be implemented when use of the IC in a special mode where the absolute maximum ratings may be exceeded is anticipated.

#### 2. GND voltage

Ensure a minimum GND pin potential in all operating conditions. In addition, ensure that no pins other than the GND pin carry a voltage lower than or equal to the GND pin, including during actual transient phenomena.

#### 3. Thermal design

Use a thermal design that allows for a sufficient margin in light of the power dissipation (Pd) in actual operating conditions.

#### 4. Inter-pin shorts and mounting errors

Use caution when orienting and positioning the IC for mounting on printed circuit boards. Improper mounting may result in damage to the IC. Shorts between output pins or between output pins and the power supply and GND pin caused by the presence of a foreign object may result in damage to the IC.

## 5. Operation in strong electromagnetic field

Operation in a strong electromagnetic field may cause malfunction.

#### 6. Thermal shutdown circuit (TSD circuit)

This IC incorporates a built-in thermal shutdown circuit (TSD circuit). The TSD circuit is designed only to shut the IC off to prevent runaway thermal operation. Do not continue to use the IC after operating this circuit or use the IC in an environment where the operation of the thermal shutdown circuit is assumed.

#### 7. Testing on application boards

When testing the IC on an application board, connecting a capacitor to a pin with low impedance subjects the IC to stress. Always discharge capacitors after each process or step. Ground the IC during assembly steps as an antistatic measure, and use similar caution when transporting or storing the IC. Always turn the IC's power supply off before connecting it to or removing it from a jig or fixture during the inspection process.

#### 8. IC pin input

This IC is a monolithic IC which (as below) has P+ substrate and between the various pin. A P-N junction is formed from this P layer of each pin. For example the relation between each potential is as follows. (When GND > PinB and GND > PinA, the P-N junction operates as a parasitic diode.) Parasitic diodes can occur inevitably in the structure of the IC. The operation of parasitic diodes can result in mutual interference among circuits as well as operation faults and physical damage. Accordingly, you must not use methods by which parasitic diodes operate, such as applying a voltage that is lower than the GND(P substrate)voltage to an input pin.




Fig.34 Simplified structure of a Bipolar IC

#### 9. Common impedance

Power supply and ground wiring should reflect consideration of the need to lower common impedance and minimize ripple as much as possible (by making wiring as short and thick as possible or rejecting ripple by incorporating inductance and capacitance).

#### 10. Pin short and mistake fitting

Do not short-circuit between OUT pin and VCC pin, OUT pin and GND pin, or VCC pin and GND pin. When soldering the IC on circuit board, please be unusually cautious about theorientation and the position of the IC.




Fig.35

#### 11. Application circuit


Although we can recommend the application circuits contained herein with a relatively high degree of confidence, we ask that you verify all characteristics and specifications of the circuit as well as performance under actual conditions. Please note that we cannot be held responsible for problems that may arise due to patent infringements or noncompliance with any and all applicable laws and regulations.

#### 12. Operation


The IC will turn ON when the voltage at the STBY pin is greater than 2.0V and will switch OFF if under 0.3V. Therefore, do not input voltages between 0.3V and 2.0V. Malfunctions and/or physical damage may occur.

#### Power Dissipation


#### TO252-S



#### **TO220**





# Ordering part number




#### Package specifications


# TO252-5







#### TO220FP-5







# TO220FP-5(V5)





# **TO220CP-V5**





#### Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact us.

# **ROHM Customer Support System**

http://www.rohm.com/contact/