SPEC

Spec No.	TQ3C-8EAC0-E1DDV30-00
Date	March 13, 2007

## TYPE: KCG057QVLDG-G000

< 5.7 inch QVGA transmissive color STN with LED backlight>

#### **CONTENTS**

- 1. Application
- 2. Construction and outline
- 3. Mechanical specifications
- 4. Absolute maximum ratings
- 5. Electrical characteristics
- 6. Optical characteristics
- 7. Circuit block diagram
- 8. Interface signals
- 9. Interface timing chart
- 10. Data and screen
- 11. Input timing characteristics
- 12. Supply voltage sequence condition
- 13. Backlight characteristics
- 14. Lot number identification
- 15. Warranty
- 16. Precautions for use
- 17. Reliability test data
- 18. Outline drawing

Issued

Date: Mar.19,2007



Hayato LCD Division

KYOCERA CORPORATION KAGOSHIMA HAYATO PLANT LCD DIVISION

This specification is subject to change without notice.

Consult Kyocera before ordering.

Original		Designed by: l	Designed by: Engineering dept.			Confirmed by: QA dept.	
Issue Dat	e	Prepared	Checked	Approved	Checked	Approved	
March 13, 2	007	O. Ajisaka	J. Yomozohi	4 Matsumoto	J. Şakaguchi	To Suf	

Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	-

# Warning

- 1. This Kyocera LCD module has been specifically designed for use only in electronic devices and industrial machines in the area of audio control, office automation, industrial control home appliances, etc. The module should not be used in applications where the highest level of safety and and reliability are required and module failure or malfunction of such module results in physical harm or loss of life, as well as enormous damage or loss. Such fields of applications include, without limitation, medical, aerospace, communications infrastructure, atomic energy control. Kyocera expressly disclaims any and all liability resulting in any way to the use of the module In such applications.
- 2. Customer agrees to indemnity, defend and hold Kyocera harmless from and against any and all actions, claims, damages, liabilities, awards, costs, and expenses, including legal expenses, resulting from or arising out of Customer's use, or sale for use, or Kyocera modules in applications.

#### Caution

1. Kyocera shall have the right, which Customer hereby acknowledges, to immediately scrap or destroy tooling for Kyocera modules for which no Purchase Orders have been received from the Customer in a two-year period.



Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	-

## Revision record

Date		Designe		Engineering of		Confirmed by	: QA dept.
		Prepa	red	Checked	Approved	Checked	Approved
D 11	D :	ъ т			D		
Rev.No.	Date	Page			Descripti	ons	



Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	1

# 1. Application

This document defines the specification of KCG057QVLDG-G000. (RoHS Compliant)

#### 2. Construction and outline

LCD : Transmissive color dot matrix type STN

Duty ratio : 1/240 duty Backlight system : LED

Polarizer : Glare treatment

Additional circuit : Bias voltage circuit, Randomizing circuit,

DC/DC converter circuit, Temperature compensation circuit

#### 3. Mechanical specifications

Item	Specification	
Outline dimensions	144 (W)× (104.8) (H) × 12.7 (D)	mm
Active area	115.18 (W) × 86.38 (H) (14.4cm / 5.7 inch (Diagonal))	
Effective viewing area	fective viewing area $117.2 \text{ (W)} \times 88.4 \text{ (H)}$	
Dot format	320×(R,G,B) (W) × 240 (H)	dot
Dot size $0.10 \text{ (W)} \times 0.34 \text{ (H)}$		mm
Dot pitch	0.12 (W) × 0.36 (H)	mm
Base color *1	Normally Black	
Mass	175	g

<sup>\*1</sup> Due to the characteristics of the LCD material, the color varies with environmental temperature.



Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	2

#### 4. Absolute maximum ratings

#### 4-1. Electrical absolute maximum ratings

Item	Symbol	Min.	Max.	Unit
Supply voltage for logic	$V_{ m DD}$	0	6.0	V
Supply voltage for LCD driving	$V_{\rm CONT}$	0	$ m V_{DD}$	V
Input signal voltage *1	$V_{\rm IN}$	0	$ m V_{DD}$	V
FRM frequency	${ m f}_{ m FRM}$	-	150	$_{ m Hz}$
LED forward current *2	IF	-	27	mA
Reversed voltage *2	VR	-	5	V

<sup>\*1</sup> Input signal : FRM, LOAD, CP, DISP, D0 ~ D7

#### 4-2. Environmental absolute maximum ratings

Item		Symbol	Min.	Max.	Unit
Operating temperature	*1	$T_{OP}$	0	60	$^{\circ}\mathrm{C}$
Storage temperature	*2	Tsto	-20	60	$^{\circ}\mathrm{C}$
Operating humidity	*3	$H_{\mathrm{OP}}$	10	*4	%RH
Storage humidity	*3	Hsto	10	*4	%RH
Vibration		-	*5	*5	-
Shock		-	*6	*6	-

<sup>\*1</sup> Operating temperature means a temperature which operation shall be guaranteed. Since display performance is evaluated at 25°C, another temperature range should be confirmed.

Store LCD panels at normal temperature/humidity. Keep them free from vibration and shock. An LCD panel that is kept at a low or a high temperature for a long time can be defective due to other conditions, even if the low or high temperature satisfies the standard.

(Please refer to "Precautions for Use" for details.)

Temp. > 40°C, Absolute humidity shall be less than 85%RH at 40°C.

\*5

Frequency	10 ~ 55 Hz	Acceleration value
Vibration width	0.15mm	$(0.3 \sim 9 \text{ m/s}^2)$
Interval	10-55-10	Hz 1 minutes

2 hours in each direction X, Y, Z (6 hours total)

**EIAJ ED-2531** 

\*6 Acceleration: 490 m/s², Pulse width: 11 ms

3 times in each direction:  $\pm X$ ,  $\pm Y$ ,  $\pm Z$ 

**EIAJ ED-2531** 



<sup>\*2</sup> For each "AN1-CA1", "AN2-CA2" and "AN3-CA3"

<sup>\*2</sup> Temp. = -20°C < 48h, Temp. = 60°C < 168h

<sup>\*3</sup> Non-condensing

<sup>\*4</sup> Temp. 40°C, 85%RH Max.

Spec No.		Part No.	Page
TQ3C-8EA	C0-E1DDV30-00	KCG057QVLDG-G000	3

#### 5. Electrical characteristics

 $5-1. V_{DD} = 5.0V$ 

 $V_{DD} = +5.0V \pm 5\%$ , Temp. =  $0 \sim 60$ °C

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Supply voltage for logic	$V_{ m DD}$	-	4.75	5.00	5.25	V
Supply voltage for LCD driving	V	0~50°C *3	1.30	1.80	2.30	V
*1, *2	V <sub>CONT</sub> = V <sub>OP</sub>	~ 60°C	-	-	2.40	V
Input signal voltage	<b>V</b>	"High" level	$0.8 V_{\mathrm{DD}}$	-	$V_{ m DD}$	V
(FRM,LOAD,CP,DISP,D0 ~ D7)	$ m V_{IN}$	"Low" level	0	-	$0.2 V_{ m DD}$	V
Input current	${ m I}_{ m IN}$	Input signal	-100	-	100	μA
Rush current for logic	I <sub>RUSH</sub>	When LCD turn on.		3.0A (Peak	x) × 1ms	
Clock frequency	$\mathbf{f}_{\mathrm{CP}}$	-	-	-	10.00	MHz
Frame frequency *4	${ m f}_{ m FRM}$	-	70	75	80	$_{ m Hz}$
Current consumption for logic	${ m I}_{ m DD}$	*5	-	27	41	mA
Power consumption	$\mathrm{P}_{\mathrm{DISP}}$	9	-	135	203	mW

<sup>\*1</sup> Maximum contrast ratio is obtained by adjusting the LCD supply voltage ( $V_{CONT} = V_{OP}$ ) for driving the LCD.

# \*5 Display pattern:

```
VDD = 5.0V, VCONT = VOP, fFRM = 75Hz, fCP = 2.16MHz, Temp. = 25°C

1 2 3 4 5 6 · · · · · · · · · · · · · 960(dot)

1
2
3
:
:
:
239
240
(dot)
```



<sup>\*2</sup> Frame frequency :  $f_{FRM} = 75Hz$ 

<sup>\*3</sup> The LCD module has a temperature compensation circuit.

<sup>\*4</sup> In consideration of display quality, it is recommended that frame frequency be set in the range of 70-80Hz. When you have to use higher frame and clock frequencies, confirm the LCD's performance and quality prior to finalizing the frequency value. Generally, as frame and clock frequencies become higher current consumption increases and display quality will degrade.

Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	4

 $5-2. V_{DD} = 3.3V$ 

 $V_{DD} = +3.3V \pm 0.3V$ , Temp. =  $0 \sim 60$ °C

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Supply voltage for logic	$ m V_{DD}$	-	3.0	3.3	3.6	V
Supply voltage for LCD driving	77 –77	0~50°C *3	1.30	1.80	2.30	V
*1, *2	$V_{CONT}=V_{OP}$	~ 60°C	-	-	2.40	V
Input signal voltage	<b>17</b>	"High" level	$0.8V_{\mathrm{DD}}$	•	$V_{ m DD}$	V
(FRM,LOAD,CP,DISP,D0 ~ D7)	$ m V_{IN}$	"Low" level	0	-	$0.2 V_{ m DD}$	V
Input current	${ m I_{IN}}$	Input signal	-100	-	100	μA
Rush current for logic	$I_{ m RUSH}$	When LCD turn on.		3.0A (Peak	x) × 1ms	
Clock frequency	$\mathbf{f}_{\mathrm{CP}}$	-	-	-	10.00	MHz
Frame frequency *4	$ m f_{FRM}$	-	70	75	80	Hz
Current consumption for logic	${ m I}_{ m DD}$	*5	-	41	61	mA
Power consumption	$P_{\mathrm{DISP}}$	9	-	134	201	mW

<sup>\*1</sup> Maximum contrast ratio is obtained by adjusting the LCD supply voltage (V<sub>CONT</sub>=V<sub>OP</sub>) for driving the LCD.

#### \*5 Display pattern:



<sup>\*2</sup> Frame frequency :  $f_{FRM} = 75Hz$ 

<sup>\*3</sup> The LCD module has a temperature compensation circuit.

<sup>\*4</sup> In consideration of display quality, it is recommended that frame frequency be set in the range of 70-80Hz. When you have to use higher frame and clock frequencies, confirm the LCD's performance and quality prior to finalizing the frequency value. Generally, as frame and clock frequencies become higher current consumption increases and display quality will degrade.

Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	5

# 6. Optical characteristics


Measuring spot = 6.0mm, Temp. = 25°C

					ng spot – o	то	
Item		Symbol	Condition	Min.	Typ.	Max.	Unit
D (:	Rise	τr	= =0°	-	180	280	ms
Response time	Down	τd	= =0°	-	170	270	ms
		UPPER		-	20	-	1
77 1		LOWER	CD 0	-	35	-	deg.
Viewing angle	range	LEFT	CR 2	-	50	-	1
Contrast ratio		φ right		-	50	-	deg.
Contrast ratio		CR	= =0°	30	55	-	-
Brightness		L	IF=25mA/Line	110	180	-	cd/m <sup>2</sup>
_	D. J	X	= =0°	0.45	0.50	0.55	
	Red	У	0	0.31	0.36	0.41	
	C	X	= =0°	0.25	0.30	0.35	
Chromaticity	Green	У	0	0.46	0.51	0.56	
coordinates	Dlass	X	= =0°	0.10	0.15	0.20	-
	Blue	У	U	0.07	0.12	0.17	
	<b>XX71</b> - 14 -	X	= =0°	0.24	0.29	0.34	
	White	У	U <sup>-</sup>	0.26	0.31	0.36	

Optimum contrast is obtained by adjusting the LCD driving voltage ( $V_{OP}$ ) while at the viewing angle of  $==0^{\circ}$ .


## 6-1. Definition of contrast ratio

#### 6-2. Definition of VOP







## 6-3. Definition of response time



## 6-4. Definition of viewing angle



# 6-5. Brightness measuring points




- 1) Rating is defined on the average in the viewing area.
- 2) Measured 30 minutes after the CFL is powered on. (Ambient temp. = 25°C)
- 3) Backlight : IF=25mA / 1 LED line




Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	7

# 7. Circuit block diagram



## 7-1. Power supply





Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	8

# 8. Interface signals

# 8-1. Pin assignment of LCD panel

No.	Symbol	Description	Level
1	FRM	Synchronous signal for driving scanning line	Н
2	LOAD	Data signal latch clock	$\mathrm{H}  ightarrow \mathrm{L}$
3	CP	Data signal shift clock	$\mathrm{H}  ightarrow \mathrm{L}$
4	DISP	Display control signal	H(ON),L(OFF)
5	$V_{ m DD}$	Power supply for logic	-
6	$V_{\mathrm{SS}}$	GND	-
7	$V_{\rm CONT}$	LCD adjust voltage	-
8	D7		
9	D6		
10	D5		
11	D4	D'a dan data	H(OM) I (OEE)
12	D3	Display data	H(ON),L(OFF)
13	D2		
14	D1		
15	D0		
16	$V_{ m DD}$	Down supply for logic	_
17	$V_{ m DD}$	Power supply for logic	-
18	$V_{\rm SS}$		
19	$V_{\rm SS}$	GND	-
20	$V_{\rm SS}$		

LCD connector : 08-6210-020-340-800+ (ELCO)

Recommended matching FFC or FPC : 0.5mm pitch

#### 8-2. Pin assignment of LED

No.	Symbol	Description
1	AN1	Anode 1
2	AN2	Anode 2
3	AN3	Anode 3
4	CA1	Cathode 1
5	CA2	Cathode 2
6	CA3	Cathode 3

LCD side connector : SHLP-06V-S-B (JST)

Recommended matching connector


: SM06B-SHLS-TF (JST)

: SM06B-SHLS-TF(LF)(SN) (JST)···(RoHS Compliant)



Ī	Spec No.	Part No.	Page
	TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	9

# 9. Interface timing chart



<sup>\*</sup> The cycle of the LOAD signal should be stable and continuously applied without interruption.




<sup>\*</sup> The above-mentioned timing chart is a reference to set up a LCD module, not an electrical rating.


Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	10

# 10. Data and screen

		D4 D3	D2	D1	$\mathbf{D} \circ \mathbf{D}$	_			
ID1 IC1 ID1 ID0 IC0 ID0 ID0 IC0 ID0 I ID00/IC00/ID0									D0
R1 G1 B1 R2 G2 B2 R3 G3 B3 R320 G320 B3	1 B1	R2 G2	B2	R3	G3 B	3	R320	G320	B32
		•							

# 11. Input timing characteristics







Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	11

# 11-1. Switching characteristics ( $V_{DD} = 5.0V$ )

Input characteristics :  $V_{DD} = \pm 5.0 V \pm 5\%$ , Temp. =  $0 \sim 60 ^{\circ} C$ 

Item		Symbol	Min.	Max.	Unit
CP cycle	*1	tCCL	100	-	ns
CP "H" pulse width		tWCLH	30	-	ns
CP "L" pulse width		tWCLL	30	-	ns
CP rise up time		$\operatorname{trCP}$	-	15	ns
CP fall down time		tfCP	-	15	ns
Data set up time		tDS	25	-	ns
Data hold time		tDH	25	-	ns
LOAD "H" pulse width		tWLPH	40	-	ns
LOAD "L" pulse width		tWLPL	400	-	ns
LOAD cycle	*2	tLCL	500	-	ns
$CP \rightarrow LOAD$ delay time		tCDLD	60	-	ns
$LOAD \rightarrow CP$ delay time		tLDCR	60	-	ns
Input signal rise up time		tr	-	20	ns
Input signal fall down time		tf	-	20	ns
FRM data set up time		tFS	120	-	ns
FRM data hold time		tFH	30	-	ns

<sup>\*1</sup> CP cycle is adjusted so that FRM signal is 75Hz.

# 11-2. Switching characteristics ( $V_{DD} = 3.3V$ )

Input characteristics :  $V_{DD}$  = +3.3V ± 0.3V, Temp. = 0 ~ 60°C

Item	Symbol	Min.	Max.	Unit
CP cycle *1	tCCL	100	-	ns
CP "H" pulse width	tWCLH	40	-	ns
CP "L" pulse width	tWCLL	40	-	ns
CP rise up time	$\operatorname{trCP}$	-	20	ns
CP fall down time	tfCP	-	20	ns
Data set up time	tDS	35	-	ns
Data hold time	tDH	35	-	ns
LOAD "H" pulse width	tWLPH	50	-	ns
LOAD "L" pulse width	tWLPL	400	-	ns
LOAD cycle *2	tLCL	500	-	ns
$CP \rightarrow LOAD$ delay time	tCDLD	60	-	ns
$LOAD \rightarrow CP$ delay time	tLDCR	80	-	ns
Input signal rise up time	tr	-	20	ns
Input signal fall down time	tf	-	20	ns
FRM data set up time	tFS	120	-	ns
FRM data hold time	tFH	30	-	ns

<sup>\*1</sup> CP cycle is adjusted so that FRM signal is 75Hz.




<sup>\*2</sup> LOAD cycle is constant.

<sup>\*2</sup> LOAD cycle is constant.

Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	12

# 12. Supply voltage sequence condition

In normal operation, logic within the LCD module reverses the polarity of the drive voltage every few lines to prevent DC damage to the liquid crystal material. But when a voltage is present on  $V_{\text{CONT}}$  outside of the time when the  $V_{\text{DD}}$  logic voltage is stable, a drive voltage is applied to the liquid crystal material without the polarity reversals. This sometimes result in a deterioration of display quality and a reduction in life time.



- \* Input signal: FRM, LOAD, CP, D0 ~ D7
- \* The above sequence should be designed as to maintain each normal voltage when the liquid crystal module load is applied to your system.
- \* Control the supply voltage sequence to not float any signal line when the LCD panel is being driven.



Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	13

# 13. Backlight characteristics

# LED ratings

Item		Symbol	Min.	Тур.	Max.	Unit	Note
Forward current	*1	IF	•	25	-	mA	Ta=0 ~ 60°C
			-	23.8	26.6	V	IF=25mA, Ta=0
Forward voltage	<b>*</b> 1	VF	-	23.1	25.9	V	IF=25mA, Ta=25
			-	22.3	25.1	V	IF=25mA, Ta=60
Operating life time	*2, *3	Т	1	(50,000)	-	h	IF=25mA, Ta=25

<sup>\*1</sup> For each "AN1-CA1", "AN2-CA2" and "AN3-CA3"



<sup>\*2</sup> When brightness decrease 50% of initial brightness.

<sup>\*3</sup> Life time is estimated data.

<sup>\*</sup> An input current below 8.0mA may reduce the brightness uniformity of the LED backlight. This is because the amount of light from each LED chip is different. Therefore, please evaluate carefully before finalizing the input current.

Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	14

#### 14. Lot number identification

The lot number shall be indicated on the back of the backlight case of each LCD.

No1. - No5. above indicate

- 1. Year code
- 2. Month code
- 3. Date
- 4. Version Number
- 5. Country of origin (Japan or China)

Year	2007	2008	2009	2010	2011	2012
Code	7	8	9	0	1	2

Month	Jan.	Feb.	Mar.	Apr.	May	Jun.
Code	1	2	3	4	5	6

Month	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Code	7	8	9	X	Y	Z

#### 15. Warranty

# 15-1. Incoming inspection

Please inspect the LCD within one month after your receipt.

#### 15-2. Production warranty

Kyocera warrants its LCD's for a period of 12 months from the ship date. Kyocera shall, by mutual agreement, replace or re-work defective LCD's that are shown to be Kyocera's responsibility.



Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	15

#### 16. Precautions for use

#### 16-1. Installation of the LCD

- 1) The LCD module has a grounding hole. Please ground the module to prevent noise and to stabilize its performance as circumstances demand.
- A transparent protection plate shall be added to protect the LCD and its polarizer.
- 3) The LCD shall be installed so that there is no pressure on the LSI chips.
- 4) The LCD shall be installed flat, without twisting or bending.
- 5) The display window size should be the same as the effective viewing area.
- 6) Please refer to the following our recommendable value of Clamp-down torque when installing. Clamp-down torque: 0.32±0.03N·m

Please set up 'SPEED-LOW', 'SOFT START-SLOW' when using electric driver.

Recommendable screw JIS tapping screw two types nominal dia.3.0mm installing boss hole depth 3.5±0.5mm

Please be careful not to use high torque which may damage LCD module in installation.

7) A transparent protection sheet is attached to the polarizer. Please remove the protection film slowly before use, paying attention to static electricity.

#### 16-2. Static electricity

- 1) Since CMOS ICs are mounted directly onto the LCD glass, protection from static electricity is required.
- 2) Workers should use body grounding. Operator should wear ground straps.

#### 16-3. LCD operation

- 1) The LCD shall be operated within the limits specified. Operation at values outside of these limits may shorten life, and/or harm display images.
- 2) Adjust the "Supply voltage for LCD driving (VCONT)" to obtain optimum viewing angle and contrast ratio.

#### 16-4. Storage

- 1) The LCD shall be stored within the temperature and humidity limits specified. Store in a dark area, and protect the LCD from direct sunlight or fluorescent light.
- 2) Always store the LCD so that it is free from external pressure onto it.

#### 16-5. Usage

- 1) <u>DO NOT</u> store in a high humidity environment for extended periods. Polarizer degradation bubbles, and/or peeling off of the polarizer may result.
- 2) The front polarizer is easily scratched or damaged. Prevent touching it with any hard material, and from being pushed or rubbed.
- 3) The LCD screen may be cleaned by wiping the screen surface with a soft cloth or cotton pad using a little Ethanol.
- 4) Water may cause damage or discoloration of the polarizer. Clean condensation or moisture from any source immediately.
- 5) Always keep the LCD free from condensation during testing. Condensation may permanently spot or stain the polarizer.
- 6) Do not pull the LED lead wires and do not bend the root of the wires. Housing should be designed to protect LED lead wires from external stress.
- 7) Do not disassemble LCD module because it will result in damage.
- 8) This Kyocera LCD module has been specifically designed for use in general electronic devices, but not for use in a special environment such as usage in an active gas. Hence, when the LCD is supposed to be used in a special environment, evaluate the LCD thoroughly beforehand and do not expose the LCD to chemicals such as an active gas.
- 9) Please do not use solid-base image pattern for long hours because a temporary afterimage may appear. We recommend using screen saver etc. in cases where a solid-base image pattern must be used.
- 10) Liquid crystal may leak when the module is broken. Be careful not to let the fluid go into your eyes and mouth. In the case the fluid touches your body; rinse it off right away with water and soap.



Spec No.	Part No.	Page
TQ3C-8EAC0-E1DDV30-00	KCG057QVLDG-G000	16

# 17. Reliability test data

Test item	Test condition	Test time	Jud	gement
High temp. atmosphere	70°C	240h	Display function Display quality Current consumption	: No defect : No defect : No defect
Low temp. atmosphere	-20°C	240h	Display function Display quality Current consumption	<ul><li>: No defect</li><li>: No defect</li><li>: No defect</li></ul>
High temp. humidity atmosphere	40°C 90% RH	240h	Display function Display quality Current consumption	: No defect : No defect : No defect
Temp. cycle	-20°C 0.5h R.T. 0.5h 70°C 0.5h	10cycles	Display function Display quality Current consumption	<ul><li>: No defect</li><li>: No defect</li><li>: No defect</li></ul>
High temp. operation	60°C	500h	Display function Display quality Current consumption	<ul><li>No defect</li><li>No defect</li><li>No defect</li></ul>

<sup>\*</sup> Each test item uses a test LCD only once. The tested LCD is not used in any other tests.




<sup>\*</sup> The LCD is tested in circumstances in which there is no condensation.

<sup>\*</sup> The reliability test is not an out-going inspection.

<sup>\*</sup> The result of the reliability test is for your reference purpose only.

The reliability test is conducted only to examine the LCD's capability.



Spec No.	TQ3C-8EAC0-E2DDV30-00
Date	March 13, 2007

# **KYOCERA INSPECTION STANDARD**

 $\mathbf{TYPE}: \mathbf{KCG057QVLDG\text{-}G000}$ 

KYOCERA CORPORATION KAGOSHIMA HAYATO PLANT LCD DIVISION

Original	Designed by: Engineering dept. Confirmed by: QA dept.			: QA dept.	
Issue Date	Prepared	Checked	Approved	Checked	Approved
March 13, 2007	O. Ajisaka	J. Yanazahi	4 Matsumoto	J. Sakaguchi	To Suf



Spec No.	Part No.	Page
TQ3C-8EAC0-E2DDV30-00	KCG057QVLDG-G000	-

# Revision record

Date    Designed by Engineering dept.   Commined by QAC   Prepared   Checked   Approved   Checked   App	1
Trepared Checked Approved Checked App	roved
Rev.No. Date Page Descriptions	



Spec No.	Part No.	Page
TQ3C-8EAC0-E2DDV30-00	KCG057QVLDG-G000	1

# Visuals specification 1) Note

Item		Note		
General	1.When defects specified In this Inspection Standards are inspected, operating voltage (V <sub>OP</sub> ) shall be set at the level where optimized contrast is available. Display quality is applied up to effective viewing area. (Bi-level INSPECTION)			
	2. This inspection standard about the image quality shall be applied to any defect within the effective viewing area and shall not be applicable to outside of the area.			
		h are not specified in this standard lard shall be determined by mutual mer and Kyocera.		
	Inspection distance : Temperature :	500 Lux minimum. 300 mm(from the sample) 25±5°C right above		
D. C	Di la Diale	- m 1 e 11 ·		
Definition of inspection item	Pinhole, Bright spot Black spot, Scratch Foreign particle	The color of a small area is different from the remainder. The phenomenon does not change with voltage.		
	Contrast variation	The color of a small area is different from the remainder. The phenomenon change with voltage.		
	Polarizer (Scratch, Bubble, Dent)	Scratch, Bubble and Dent in the polarizer which can be observed in on / off state.		



Spec No.	Part No.	Page
TQ3C-8EAC0-E2DDV30-00	KCG057QVLDG-G000	2

#### 2)Standard

Inspection item		Judg	ement stand	ard	
Pinhole, Bright spot, Black spot, Foreign particle			d = ( a -	ı b ) / 9	
	Category	Size(n		Acceptable nu	mhon
	A	d		Neglected	
	В	0.2 < d		5	-
	С	0.3 < d		3	
	D	0.5 < d		0	
Scratch, Foreign particle		\ <b>X</b> I7			
		L			
	V	Vidth (mm)	Length (r	nm) Accept	
	A	W 0.03	-	Negle	
	В		L	2.0 Negle	cted
	C 0.03 <	< W 0.10	2.0 < L	4.0 3	
	D		4.0 < L	0	
	E 0.10	< W	-	Accordi 'Circu	
Contrast variation	a	b	d = (a+1	n)/2	
			α (α . )	5 / 1 <b>2</b>	
	Catagagg	Cinc (	(mm)	Aggentable	mhon
	Category	Size (		Acceptable nu	
	Category A B	Size ( d	0.5	Acceptable number Neglected	



Spec No.	Part No.	Page
TQ3C-8EAC0-E2DDV30-00	KCG057QVLDG-G000	3

Inspection item		Judg	ement standa	ard
Polarizer Scratch, Bubble, Dent)	(1) Scratch			
		L	W	
	v	Vidth (mm)	Length (n	nm) Acceptable No.
	A	W 0.1	-	Neglected
	В	< W 0.3	L	5.0 Neglected
	С 0.1	· w 0.9	5.0 < L	0
	D 0.3	< W	-	0
		( <u>a</u> )	b	
		a	↓	= (a + b) / 2
	Category	Size (	d mm)	Acceptable number
	Category A	d	dmm) 0.2	
	A B	0.2 < d	dmm) 0.2 0.3	Acceptable number Neglected 5
	A	d	mm) 0.2 0.3 0.5	Acceptable number Neglected

