

# **EM511**

### **Energy analyzer for 1-phase systems**



### Description

EM511 is an energy analyser for 1-phase systems up to 240 V L-N and current up to 45 A. In addition to a digital input, the unit can be equipped, according to the model, with a static output (pulse or alarm), a Modbus RTU communication port or an M-Bus communication port.

### Benefits

- Enhanced readability. The backlit display ensures perfect visibility even in low light. The different sizes of the digits preceding and following the dot make the displayed values easier to read, while the essential style of the units of measure allows you to readily understand the available variables.
- Easy browsing. Page configuration and browsing are very intuitive, thanks to the user interface with 2 mechanical keys. The slideshow function automatically displays the desired measurements in sequence, without having to use the keyboard; the page filter allows you to hide unnecessary information.
- Quick configuration. The configuration wizard which runs when the system is started up for the first time allows you to commission the unit without errors in a matter of seconds. The UCS configuration software is available for download free of charge.
- Accurate measuring. EM511 complies with the accuracy international standard EN IEC 62053-21, EN 50470-3 and with the performance requirements (power and active energy) set out by EN IEC 61557-12.
- Fiscal metrology. EM511 can be sealed to prevent any tampering with the connections, allowing the unit, thanks to the MID certification, to perform measurements for fiscal purposes and a reinforced protection toward the power terminals.
- Bidirectional. Both imported and exported energy meters (kWh+ and kWh-) are MID certified.

### **Applications**

EM511 can be installed in any low-voltage switchboard with a rated current up to 45 A, thanks to the 10 mm<sup>2</sup> / 7 AWG screw terminals, to monitor the energy consumption, the main electrical variables and the harmonic distortion.

If used to monitor a single machine or a specific load, it provides all the main electrical variables to identify any possible malfunction in its early stage and can correlate the energy consumption with the hours of operation, to plan maintenance and prevent failures. The partial meter reset function, easily implementable by means of a digital input, allows you to monitor each machine cycle.

Dedicated versions able to operate up to 70  $^{\circ}$ C / 158  $^{\circ}$ F (S1PFx70 models), are the best solution for installation in electric vehicles chargers placed outdoors and exposed to high temperature or direct solar radiation.

The MID-certified versions can be used for fiscal metrology and can be installed in residential or commercial buildings to split the costs among the different units, or as a component of machines or equipment requiring measurement certification. The standard versions (S1X, S1XB), thanks to their extended resolution, are also suited for EV chargers addressed to the US market, where CTEP and cULus approvals are needed.



Thanks to the fast communication refresh time and the high resolution of the variables, EM511 can also be used as a data source for control actions, such as avoiding feeding energy into the electricity grid in a photovoltaic joint installation with energy storage.



### **Main functions**

- Measure active, reactive and apparent energy
- Measure the main electrical variables
- · Measure the load run hours
- Measure the total harmonic distortion (THD) of current and voltage
- Transmit data to other systems through Modbus RTU or M-Bus
- · Manage a digital output for pulses or alarm transmission
- · Visualize the measured variables on the display




### Main features


- Real time variables (V L-N, A, W/var, VA, PF, Hz)
- Displaying the consumed active energy with a resolution of 0.001 kWh
- The frequency value is available via Modbus, with a resolution of 0.001 Hz
- Average value calculation (dmd) for current and power (kW/kVA)
- Modbus RTU RS485 or M-Bus communication (data refresh every 100 ms)
- Continuous sampling of voltage and current
- · Backlit LCD display
- MID-certified meter resolution 0.001 kWh
- cULus approved (UL 61010)
- Serial communication meter resolution 0.0001 kWh (S1X, S1XB models only), suited for CTEP approved chargers (US market)
- Compliance with the performance requirements set out by EN IEC 61557-12 (power and active energy)
- Operating temperature up to 70°C / 158°F (S1PFx70 models)



### **UCS** software

- Free download from Carlo Gavazzi website
- Configuration through RS485 from PC or through UWP3.0/UWP4.0 via LAN or the web (UWP Secure Bridge function)
- Setups can be saved offline for serial programming with a single command
- · Real time data view for testing and diagnostics







# **Structure**




Fig. 1 Front


Area	Description
Α	Voltage inputs / Current inputs
В	DIN rail mounting bracket
С	Display
D	Digital input, digital output and communication connections
Е	LED
F	Sealable covers
G	Browsing and configuration buttons



# **Features**

# General

	Housing: PBT			
Material	Transparent cover: polycarbonate			
III flommobility close	Housing: V-0			
UL flammability class	Transparent cover: V-2			
Protection degree	Front: IP40			
Protection degree	Terminals: IP20			
	Measurement inputs: 2.5 to 10 mm <sup>2</sup> / 7 to 13 AWG, 1.1 Nm / 9.74 lbin			
Terminals	Inputs, outputs and communication: 0.2 to 2.5 mm $^2$ / 13 to 24 AWG, 0.4 to 0.8 Nm / 3.54 to 7.08 lbin			
Overvoltage category	Cat. III			
Pollution degree	2			
Mounting	DIN rail			
Weight	155 g / 0.34 lb (packaging included)			





## **Environmental specifications**

Operating temperature	From -25 to +55 °C / from -13 to +131 °F (X, XB, PFx and SFA models) From -25 to +70 °C / from -13 to +158 °F (S1PFx70 models)
Storage temperature	From -25 to +70 °C / from -13 to +158 °F
Electromechanical environmental condition	E2
Mechanical envir- onmental condition	M2

**Note**: R.H. < 90 % non-condensing @ 40 °C / 104 °F.

## Input and output insulation

Туре	Measurement inputs	Digital input	Digital output	RS485 serial port	M-Bus serial port
Measurement inputs	-	Double/Reinforced	Double/Reinforced	Double/Reinforced	Double/Reinforced
Digital input	Double/Reinforced	-	none	none	none
Digital output	Double/Reinforced	none	-	-	-
RS485 serial port	Double/Reinforced	none	-	-	-
M-Bus serial port	Double/Reinforced	none	-	-	-

According to: EN 61010-1, EN 50470-1 (MID). Overvoltage category III. Pollution degree 2.

## Compatibility and conformity

Directives	2014/32/EU (MID) 2014/35/EU (LVT - Low Voltage) 2014/30/EU (EMC - Electro Magnetic Compatibility) 2011/65/EU (Electric-electronic equipment hazardous substances)
Standards	Electromagnetic compatibility (EMC) - emissions and immunity: EN IEC 62052-11, EN 50470-1 (MID)  Electrical safety: EN IEC 61010-1, EN 50470-1 (MID)  Metrology: EN IEC 62053-21, EN IEC 62053-23, EN 50470-3 (MID), EN IEC 61557-12 (active power and active energy, MID models only)  Pulse output: EN IEC 62053-31
Approvals	C E c UL LISTED



# Electrical specifications

Electrical system	
Managed electrical	Single-phase
system	

Voltage inputs - MID		
Voltage connection	Direct	
Rated voltage L-N	230 V	
Voltage tolerance	From 0.8 to 1.15 Un	
Input impedance	Refer to "Power supply"	
Frequency	50 Hz	

Voltage inputs - non MID		
Voltage connection	Direct	
Rated voltage L-N (from Un min to Un max)	120 to 240 V	
Voltage tolerance	From 0.8 to 1.15 Un	
Input impedance	Refer to "Power supply"	
Frequency	50/60 Hz	

Current inputs		
Current connection	Direct	
Base current (lb)	5 A	
Minimum current (Imin)	0.25 A	
Maximum current (Imax)	45 A	
Start-up current (Ist)	0.02 A	
Overload	For 10 ms: 30 lmax (1350 A)	
Input impedance	<1.4 VA	
Crest factor	2.5	

# Power supply

Туре	Self power supply
Consumption	< 0.6 W / 1.8 VA



### Measurements

Method	TRMS measurements of distorted waveforms
Compling	1600 samples/s @50 Hz
Sampling	1920 samples/s @60 Hz

# Available measurements

Active energy	Unit
Imported (+) Total	kWh+
Imported (+) partial	kWh+
Exported (-) Total	kWh-
Exported (-) partial	kWh-
Imported (+) tariff 1	kWh+
Imported (+) tariff 2	kWh+

Reactive energy	Unit	
Imported (+) Total	kvarh+	
Imported (+) partial	kvarh+	
Exported (-) Total	kvarh-	
Exported (-) partial	kvarh-	

Apparent energy	Unit	
Total	kVAh	
Partial	kVAh	

Run hour meter	Unit	
Total (kWh+)	hh:mm	
Partial (kWh+)	hh:mm	
Total (kWh-)	hh:mm -	
Partial (kWh-)	hh:mm -	
Total ON time	hh:mm	

Electrical variable	Unit
Voltage L-N	V
Current	A
DMD	A
DMD MAX	A
Active power	kW
DMD	kW



Electrical variable	Unit
DMD MAX	kW
Apparent power	kVA
DMD	kVA
DMD MAX	kVA
Reactive power	kvar
Power factor	PF
Frequency	Hz
THD Current*	%
THD Voltage*	%

<sup>\*</sup> Up to 15<sup>th</sup> harmonic

**Note**: total imported active energy (kWh+ TOT) and Total exported active energy (kWh- TOT) are the only MID certified meters. Apparent energy, reactive energy are not MID certified. Partial meters are not MID certified.



### **Energy metering**

Energy metering depends on the measurement type you choose (selectable in non-MID models, according to the model in MID-certified models).

### A measurement (MID PFA and SFA models)

Easy connection function: irrespective of the current direction, the power always has a plus sign and contributes to increase the positive energy meter. The negative energy meter is not available.

### B measurement (MID PFB models)

Bidirectional: according to the power sign, the positive or the negative energy meter increases.

### Measurement accuracy

Current		
From 0.5 A to 45 A	± 0.5% rdg	
From 0.25 A to 0.5 A	± 1% rdg	

Voltage	
From 0.8 Un min to 1.15 Un max	± 0.5% rdg

Active and apparent power		
From 0.5 A to 45 A (PF=0.5L, 1, 0.8C)	± 1% rdg	
From 0.25 A to 0.5 A (PF=1)	± 1.5% rdg	



Reactive power		
From 1 A to 45.0 A (sinφ=0.5L, 0.5C) From 0.5 A to 45 A (sinφ=1)	± 2% rdg	
From 0.5 A to 1.0 A (sinφ=0.5L, 0.5C) From 0.25 A to 0.5 A (PF=1)	± 2.5% rdg	

Energy		
Active energy	Class 1 (EN IEC 62053-21), Class B EN 50470-3 (MID)	
Reactive energy	Class 2 (EN IEC 62053-23)	

Frequency		
From 45 to 65 Hz	± 0.1% rdg	

### Measurement resolution

Variable	Display resolution	Resolution by serial communication	
Energy	0.001 kWh/kvarh/kVAh		
Power	0.001 kW/kvar/kVA	0.1 W/var/VA	
Current	0.001 A		
Voltage	0.1 V		
Frequency	0.001 Hz		
THD	0.01 %		
Power factor	0.01	0.001	
Hour meter	1 min		

# Display

Туре	Segments			
Refresh time	500 ms			
Description	Backlit LCD			
Instantaneous: 5+1 dgt, 5+2 dgt or 5+3 dgt				
Variable readout	Power factor: 1+3 dgt			
	Energy: 6+3 dgt			



# **LED**

Front
-------



# Digital outputs/inputs

# Digital input

Connection type	Screw terminals		
Number of inputs	1		
Туре	Free contact		
	Remote status		
Function	Tariff management		
runction	Partial meter start/pause		
	Partial meter reset		
	Open contact voltage: 5 Vdc +/- 5%		
	Closed contact current: 5 mA max		
Factures	Input impedance: 11.6 k Ω		
Features	Open contact resistance: ≥ 25 kΩ		
	Closed contact resistance: ≤ 840 Ω		
	Maximum voltage applicable with no damages: 30 V ac		
Configuration	Input function		
parameters	·		
Configuration mode	Via keypad or UCS software		

# Digital output (O1 version)

Connection type	Screw terminals			
Maximum number of outputs	1			
Туре	Opto-Mosfet			
Function	Pulse output or alarm output			
	V <sub>ON</sub> 2.5 V ac/dc, max 100 mA			
Features	V <sub>OFF</sub> 42 V ac/dc			
	Output function (pulse/alarm)			
Configuration Pulse weight (from 0.001 to 10 kWh per pulse)				
parameters	Pulse duration (30 or 100 ms)			
	Output normal status (NO or NC)			
Configuration mode	Via keypad			



# **Communication ports**

## Modbus RTU (S1 version)

Protocol	Modbus RTU			
Devices on the same bus	Max 247 (1/8 unit load)			
Communication type	Multidrop, bidirectional			
Connection type	2 wires			
Configuration parameters	Modbus address (from 1 to 247) Baud rate (9.6/19.2/38.4/115.2 kbps) Parity (None/Even)			
Refresh time	≤ 100 ms			
Configuration mode	Via keypad or UCS software			

# M-Bus (M1 version)

Protocol	M-Bus according to EN IEC 13757-3:2013			
Unit loads	1			
Connection type	2 wires			
Configuration	Primary address (from 1 to 250)			
parameters	Baud rate (0.3/2.4/9.6 kbps)			
Refresh time	≤ 100 ms			
Configuration mode	Via keypad			



# **Connection Diagrams**




Fig. 3 Single-phase system (solution A)




Fig. 4 Single-phase system (solution B)

### Digital outputs/inputs




Fig. 5 Digital input




Fig. 6 Digital output



### Communication




Fig. 7 M-Bus Fig. 8 RS485 port Fig. 9 Last device on RS485



# References

Order code			
<b>₹EM511 DIN AV8 1X</b>			
Temperature up to +55 °C / +131 °F with possibility to select different communication ports.			
Enter the code option instead of			
Code	Options	Description	

Code	Options	Description	
<b>EM511 DIN AV8 1X</b>		-	
	01	Digital output	
	<b>S1</b>	RS485 Modbus RTU	
	M1	M-Bus	
	X	Non MID model, cULus approval	
	ХВ	Non MID model, cULus approval (*)	
	SFA	MID for Switzerland and Austria, easy connection (**)	
	PFA	MID, easy connection (**)	
	PFB	MID bidirectional (***)	

# **②** EM511 DIN AV8 1X S1 □ 70

### Temperature up to +70 °C / +158 °F with RS485 Modbus RTU port.

Code	Options	Description	
<b>EM511 DIN AV8 1X</b>		-	
S1		RS485 Modbus RTU	
	PFA	MID, easy connection	
	PFB	MID bidirectional	
70		Max operating temperature	

- (\*) XB models are manufactured in Italy, the other models are all manufactured in China.
- (\*\*) PFA and SFA models: independently of the current direction, the power always has a plus sign and contributes to increase the positive energy meter. The negative energy meter is not available
- (\*\*\*) PFB models: according to the power sign, the positive or the negative energy meter increases. Both kWh+ and kWh- are MID certified meters.



# **CARLO GAVAZZI compatible components**

Purpose	Component name/code key	Notes
Configure analyzer via desktop application	UCS software	Available for free download at: www.gavazziautomation.com
Aggregate, store and transmit data to other systems	UWP 3.0, UWP 4.0	See relevant datasheet at: www.gavazziautomation.com



COPYRIGHT ©2024

Content subject to change. Download the PDF: www.gavazziautomation.com