



classic mono LCDs

SPECIFICATION CHARACTER TYPE DOT MATRIX LCD MODULE

ITEM NUMBER: ESTABLISHED DATE: INITIAL ISSUED DATE: DATASHEET VERSION: FDCC2004C-FLYYBW-51LR 1999.06 2005.05 2008 VERSION

This item supplied to Farnell by MIDAS COMPONENTS



MIDAS COMPONENTS LTD

Address: Electra House, 32 Southtown Road, Great yarmouth, Norfolk, England, NR31 ODU Email: sales@midascomponents.co.uk Website: www.midascomponents.co.uk Tel: +44 (0)1493 602602 Fax: +44 (0)1493 665111



ISSUED BY: 巍巍东 CHECKED BY: 衣命风 APPROVED BY: 是特表

COPYRIGHT © 2000 ~ 2009 FORDATA ELECTRONIC CO., LTD. ALL RIGHTS RESERVED

FORDATA ELECTRONIC CO.,LTD STANDARD PROFESSIONAL LCD SUPPLIER FROM CHINA DOC.

DATASHEET STATEMENT

- The following icons are absolutely designed by FORDATA independently in 2007-SEP. They are not in common use in the LCD industry yet but just used for marking out FORDATA products' characteristics quickly and simply without any special meaning. FORDATA reserves the composing right and copyright. No one else is allowed to adopt these icons without FORDATA's approval.
- 2. The ISO9001 logo used in this document is authorized by SGS (www.sgs.com). FORDATA had already successfully passed the strict and professional ISO9001:2000 Quality Management System Certification and got the certificate (No.: CN07/00404)
- 3. The technologies/techniques/crafts which denoted by the following icons are not exclusively owned by FORDATA, but also shared by FORDATA's LCD strategic cooperators, however all these technologies/techniques/crafts have been finally confirmed by FORDATA's professional engineers and QC department.
- 4. As the difference in test standard and test conditions, also FORDATA's insufficient familiarity with the actual LCD using environment, all the referred information in this DATASHEET (including the icons) only have two functions:
 4.1: providing quick reference when you are judging whether or not the product meets your requirements.
 4.2: listing out definitely the tolerance.

FORDATA declares seriously: you should first test the corresponding sample(s) before signing the formal FORDATA SAMPLE APPROVAL document rather than consider this DATASHEET as the standard for judging whether or not the LCD meets your requirements. Once you instruct FORDATA to a mass-production without definite demand for providing sample before, FORDATA will disclaim all responsibility if the mass-production is proved not meeting with your requirements.

- 5. The sequence of the icons is random and doesn't indicate the importance grade.
- 6. Icons explanation



FORDATA's 2006 version logo. FORDATA is an integrated manufacturer of flat panel display (FPD). FORDATA supplies TN, HTN, STN, FSTN monochrome LCD panel; COB, COG, TAB LCD module; and all kinds of LED backlight.

classic mono LCDs



FAST RESPONSE TIME

This icon on the cover indicates the product is with high response speed; Otherwise not.

C		
	HC	
Ľ		

HIGH CONTRAST

This icon on the cover indicates the product is with high contrast; Otherwise not.



WIDE VIEWING SCOPE

This icon on the cover indicates the product is with wide viewing scope; Otherwise not.



RoHS COMPLIANCE

This icon on the cover indicates the product meets ROHS requirements; Otherwise not.



3TIMEs 100% QC EXAMINATION This icon on the cover indicates the product

has passed FORDATA's thrice 100% QC. Otherwise not.



VIcm = 3.0V

This icon on the cover indicates the product can work at 3.0V exactly; otherwise not.



PROTECTION CIRCUIT

This icon on the cover indicates the product is with protection circuit; Otherwise not.



LONG LIFE VERSION

This icon on the cover indicates the product is long life version (over 9K hours guaranteed); Otherwise not.



Anti UV VERSION

This icon on the cover indicates the product is against UV line. Otherwise not.



OPERATION TEMPERATURE RANGE

This icon on the cover indicates the operating temperature range (X-Y).



TWICE SELECTION OF LED MATERIALS

This icon on the cover indicates the LED had passed FORDATA's twice strict selection which promises the product's identical color and brightness; Otherwise not.



N SERIES TECHNOLOGY (2008 developed)

FORDATA adopts new structure, new craft, new technology and new materials inside both LCD module and LCD panel to improve the "RainBow"

BOOKBINDING AREA									
FORDATA ELECTRONIC CO.,LTD PROFESSIONAL LCD SUPPLIER FROM CHINA	STANDARD DOC.	REVISION RECORD	PAGE	1/20					

NO.	DATE	DESCRIPTION	ITEM	PAGE	APPROVED
1	2005.05	INITIAL ISSUED	ALL	ALL	LU BOO
2	2007.04	Added further information of LED backlight	4	4/20	Sty &
3	2008.01	Adopt logos on the cover for fast reference	-	Cover	Et y R
4	2008.10	Deleted "N = No Ic" from CODE2	-	Code System	Stipk
5	2008.10	Added CODE "B" for DFSTN version in CODE7	-	Code System	Stipk

BOOKBINDING AREA

FORDATA ELECTRONIC CO.,LTDSTANDARDPROFESSIONAL LCD SUPPLIER FROM CHINADOC.

CODE SYSTEM

STANDARD COB

PAGE

1/1

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
FD	С	С	08	01	A	F	L	Y	Y	В	W	5	2	L	Е

No.	REMARKS	DESCRIPTION
1	COMPANY ABBRAVIATED	FD = FORDATA
2	IC packing	C = Chip On Board G = Chip On Glass T = TAB
3	LCM type	C = Character G = Graphic
	Chyaracter	08, 10, 12, 16, 20, 24, 40, = Character number Per line
4	Graphic	80, 100, 120, 122, 128, 160 = Row Dots Quantity
_	Character	01, 02, 04, = Character Lines
5	Graphic	32, 64, 80, 128, 160 =Column Dots Quantity
6	Serial Number	A~Z
7	Polarizer type	R = Positive ReflectiveF = Positive TransflectiveM = Positive TransmissiveN = Negative TransmissiveE = Negative, TransflectiveB = Negative, Dual optical compensation (for FSTN type only)
8	Backlight type	N = No BacklightS = Edge Type LED BacklightL = Array Type LED BacklightS = Edge Type LED BacklightE = EL backlight without InvertorF = EL backlight with InvertorC = CCFL backlight without InvertorT = CCFL backlight with Invertor
9	Backlight color	N = No BacklightY = Yellow-GreenW = WhiteR = RedA = AmberC = Blue-GreenB = BlueG = Green
10	LCD panel type	T = TNH = HTNY = Yellow-Green STNG = Gray STNB = Blue STNF = FSTN
11	Viewing angle	B = Bottom 6:00 T = Top 12:00 R = Right 3:00 L = Left 9:00
12	Operation temperature range	$S = 0^{\circ}C \sim 50^{\circ}C$ (Single Supply Voltage) $D = 0^{\circ}C \sim 50^{\circ}C$ (Dual Supply Voltage) $W = -20^{\circ}C \sim 70^{\circ}C$ (Single Supply Voltage) $H = -20^{\circ}C \sim 70^{\circ}C$ (Dual Supply Voltage) $T = -30^{\circ}C \sim 80^{\circ}C$ (Single Supply Voltage) $E = -30^{\circ}C \sim 80^{\circ}C$ (Dual Supply Voltage)
13	Driving Voltage	1 : VIcm = 3.0V, No / EL / CCFL Backlight or VIcm = 3.0V, VIed = LED voltage, (Via AK) 2 : VIcm = 3.6V, VIed = 5.0V (Not via AK) 3 : VIcm = 3.6V, VIed = LED voltage, (Not via AK) 4 : VIcm = 5.0V, VIed = LED voltage, (Not via AK) 5 : VIcm = 5.0V, VIed = 5.0V (Not via AK) 6 : VIcm = 5.0V, No / EL / CCFL Backlight or VIcm = 5.0V, VIed = LED voltage, (Via AK) 7 : VIcm = 3.6V, No / EL / CCFL Backlight or VIcm = 3.6V, VIed = LED voltage, (Via AK) 8 : VIcm = 3.0V, VIed = LED voltage, (Via AK) 8 : VIcm = 3.0V, VIed = 5.0V
14	Backlight Connect Method	0 = PIN1 LED-, PIN2 LED+ 1 = PIN15(17/19) LED+, PIN16(18/20) LED- 2 = PIN15(17/19) LED-, PIN16(18/20) LED+ 3 = PIN15(17/19) LED+, PIN16(18/20) NC 4 = PIN15(17/19) NC, PIN16(18/20) LED+ 5 = PINA LED+, PINK LED- 6 = No / EL / CCFL Backlight
15	IC Manufacturer	X = SAMSUNGL = SUNPLUSS = SITRONIXT = TOSHIBAE = EPSONH = HOLTEKQ = ASLICN = CIMTEKP = PRINCETON
16	Font Set	R = English - RussiaE = English - JapaneseU = English - EuropeH = English - HebrewK = English - EuropeN = NO FONT SET

	BOOKBIN	DING AREA			
	FORDATA ELECTRONIC CO.,LTD PROFESSIONAL LCD SUPPLIER FROM CHINA	STANDARD DOC.	CONTENTS	PAGE	3/20
				1	I
1.	GENERAL SPECIFICATIONS			Page	4
2.	MECHANICAL SPECIFICATIONS			Page	4
3.	ABSOLUTE MAXIMUM RATINGS			Page	4
4.	ELECTRONICAL CHARACTERIS	TIC		Page	4
5.	OPTICAL CHARACTERISTICS			Page	5
6.	ELECTRICAL SPECIFICATIONS-			Page	6
7.	EXTERNAL DIMENSION			Page	8
8.	PIN ASSIGNMENT			Page	9
9.	POWER SUPPLY			Page	9
10.	REFLECTOR OF SCREEN AND D	DRAM AD	DRESS	Page	9
11.	INSTRUCTION TABLE		F	Page 1	0
12.	INSTRUCTION DESCRIPTION		F	Page 1	1
13.	CGRAM		F	Page 1	5
14.	DDRAM		F	Page 1	5
15.	INITIALIZATION		F	Page 1	6
	INTERFACE TO MPU			•	
	FONT MAP			•	
				U	
Ίδ.	PACKING DETAIL		F	age 2	U

	BOOKBINDING AREA									
5	FORDATA ELECTRONIC CO.,LTD	PRODUCT	MODE NO.	PAGE	4/20					
ייך	PROFESSIONAL LCD SUPPLIER FROM CHINA	SPEC.	FDCC2004C-FLYYBW-51LR		4/20					

1. GENERAL SPECIFICATIONS

ITEM	NOMINAL DIMENSIONS / AVAILABLE OPTIONS
DISPLAY FORMAT	20 Characters by 4 Lines
LCD PANEL OPTIONS	STN (Yellow-green color)
POLARIZER OPTIONS	Positive, Transflective
BACKLIGHT OPTIONS	Array type LED backlight (Yellow-green color)
VIEWING ANGLE OPTIONS	6:00 (Bottom)
TEMPERATURE RANGE OPTIONS	Wide temp. range (-20°C ~ 70°C)
CONTROLLER IC	SUNPLUS
DISPLAY DUTY	1/16
DRIVING BIAS	1/5

2. MECHANICAL SPECIFICATIONS

OVERALL SIZE	LED backlight version : 77.0 x 47.0 x max 14.5							
VIEWING AREA	60.0W x 22.0H	mm	HOLE-HOLE	70.0W x 40.0H	mm			
CHARACTER SIZE	2.30W x 4.03H	mm	CHARACTER PITCH	0.48W x 0.48H	mm			
DOT SIZE	0.42W x 0.46H	mm	DOT PITCH	0.05W x 0.05H	mm			

3. ABSOLUTE MAXIMUM RATINGS

ITEM	SYMBOL	CONDITION	MIN	MAX	UNIT
POWER SUPPLY (LOGIC)	Vdd	25°C	-0.3	7.0	V
POWER SUPPLY (LCD)	V0	25°C	Vdd -13.5	Vdd +0.3	V
INPUT VOLTAGE	Vin	25°C	-0.3	Vdd +0.3	V
OPERATING TEMPERATURE	Vopr		-20	70	°C
STORAGE TEMPERATURE	Vstg		-30	80	°C

4. ELECTRONICAL CHARACTERISTIC*

ITEM	SYMBOL	CONDITION	SI	FANDA	RD	UNIT
	STWDUL	CONDITION	MIN	ТҮР	MAX	UNIT
Input voltage	Vdd	+5V	4.7	5.0	5.5	V
Supply current	ldd	Vdd=5V		1.6		mA
		-20 [°] C	4.40		5.00	
Recommended LCD driving		O°C	4.35		4.80	
voltage for normal temp.	Vdd - V0	25 [°] C	4.30	4.50	4.70	v
Version module		50°C	4.15		4.65	
		70°C	4.00		4.50	
LED forward voltage	Vf	25 [°] C	3.8	4.1	4.4	V
LED forward current	lf	25 [°] C		150		mA
LED reverse Current	Ir	25°C			150	μA
LED Peak wave length	λρ	25°C lf = 150mA	568		575	nm
LED illuminance (Without LCD)	Lv	25°C lf = 150mA	190		230	cd/m ²
LED life time		25 [°] C If = 150mA	9K**			Hours

* The above data are for reference only.


** The warranty period of FORDATA LCD module is 1YEAR counted from the date shown on the label of products.


BOOKBINDING AREA							
FORDATA ELECTRON			MODE NO.	PAGE	5/20		
PROFESSIONAL LCD SUPPLIE	R FROM CHINA	OM CHINA SPEC. FDCC2004C-FLYYBW-51LR			0,20		


5. OPTICAL CHARACTERISTIC


FOR TN TYPE LCD MOD	ULE (TA=25 °C,	, Vdd=5.0V ± 0.2	25V)			
ITEM	SYMBOL	CONDITION	MIN	ТҮР	UNIT	
VIEWING ANGLE	Φ2-Φ1	K=4	30			deg
VIEWINGANGLE	Θ	N=4	25			ueg
CONTRAST RATIO	К			2		
RESPONSE TIME(RISE)	TR			120	150	ms
RESPONSE TIME(FALL)	TF			120	150	ms

FOR STN TYPE LCD MO	DULE (TA=25 °	C, Vdd=5.0V ±0	.25V)			FOR STN TYPE LCD MODULE (TA=25 °C, Vdd=5.0V ±0.25V)													
ITEM	SYMBOL	CONDITION	MIN	ТҮР	MAX	UNIT													
VIEWING ANGLE	Φ2-Φ1	K=4	40			deg													
VIEWINGANGLE	Θ	N=4	60			ueg													
CONTRAST RATIO	К			6															
RESPONSE TIME(RISE)	TR			150	250	ms													
RESPONSE TIME(FALL)	TF			150	250	ms													









6. ELECTRICAL SPECIFICATIONS

6.1 DC CHARACTERISTICS (VDD = 4.5V to 5.5V, TA = 25 $^{\circ}\text{C}$)

CHARACTERISTICS	SYMPOL		LIMIT		UNIT	TEST CONDITION
CHARACTERISTICS	STWIDOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
INPUT HIGH VOLTAGE	VIH1	2.2		Vdd	V	Pins (E. RS. R/W. DB0 - DB7)
INPUT LOW VOLTAGE	VIL1	-0.3		0.6	V	-1113(2.103.100.000-001)
INPUT HIGH CURRENT	Іін	-2.0		2.0	μA	Pins (RS. R/W. DB0 - DB7)
INPUT LOW CURRENT	IIL	-20	-50	-100	μΑ	Vdd = 5.0V
OUTPUT HIGH VOLTAGE (TTL)	Vон1	2.4		Vdd	V	Іон = - 0.1mA Pins: DB0 - DB7
OUTPUT LOW VOLTAGE (TTL)	Vol1			0.4	V	IoL = 0.1mA Pins: DB0 - DB7

6.2 AC CHARACTERISTICS (VDD = 4.5V to 5.5V, TA = 25 °C)

Write mode


CHARACTERISTICS	SYMBOL		LIMIT		UNIT	TEST CONDITION
	STNIDUL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
ENABLE CYCLE TIME	tc	500			ns	Pin E
ENABLE PULSE WIDTH	tpw	230			ns	Pin E
ENABLE RISE/ FALL TIME	tr, tr			20	ns	Pin E
ADDRESS SETUP TIME	tsp1	40			ns	Pins RS, R/W, E
ADDRESS HOLD TIME	thd1	10			ns	Pins RS, R/W, E
DATA SETUP TIME	tsp2	80			ns	Pins: DB0 - DB7
DATA HOLD TIME	thd2	10			ns	Pins: DB0 - DB7

Read mode


CHARACTERISTICS	SVMPOL		LIMIT		UNIT	TEST CONDITION
	STIVIDUL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
ENABLE CYCLE TIME	tc	500			ns	Pin E
ENABLE PULSE WIDTH	tpw	230			ns	Pin E
ENABLE RISE/ FALL TIME	tr, tr			20	ns	Pin E
ADDRESS SETUP TIME	tsp1	40			ns	Pins RS, R/W, E
ADDRESS HOLD TIME	thd1	10			ns	Pins RS, R/W, E
DATA OUTPUT DELAY TIME	to			120	ns	Pins: DB0 - DB7
DATA HOLD TIME	thd2	5			ns	Pins: DB0 - DB7

BOOKBINI	DING AREA			
FORDATA ELECTRONIC CO.,LTD		MODE NO.	PAGE	7/20
PROFESSIONAL LCD SUPPLIER FROM CHINA	SPEC.	FDCC2004C-FLYYBW-51LR		1/20

6.3.1 WRITE MODE TIMING DIAGRAM





6.3.2 READ MODE TIMING DIAGRAM




BOOKBIN	DING AREA			
FORDATA ELECTRONIC CO.,LTD	PRODUCT	MODE NO.	PAGE	8/20
PROFESSIONAL LCD SUPPLIER FROM CHINA	SPEC.	FDCC2004C-FLYYBW-51LR		0/20

7. EXTERNAL DIMENSIONS








BOOKBINDING AREA								
FORDATA ELECTRONIC CO.,LTD PRODUCT MOD PROFESSIONAL LCD SUPPLIER FROM CHINA SPEC. FDCC2004C-I	PAGE	9/20						

8.PIN ASSIGNMENT

PIN	SYMBOL	FUNCTION
1	Vss	GND
2	Vdd	Power supply for LCM (+5.0V)
3	V0	Contrast Adjust
4	RS	Register Select Signal
5	R/W	Data Read / Write
6	E	Enable Signal
7-14	DB0 - DB7	Data bus line
15	LED+	Power supply for BKL (+5.0V)
16	LED-	Power supply for BKL (0V)

9.POWER SUPPLY



10. REFLECTOR OF SCREEN AND DDRAM ADDRESS

Display position	1-1	1-2	1-3	1-4	1-5	1-6	1-7	1-8	1-9	1-10
DDRAM address	00	01	02	03	04	05	06	07	08	09
Display position	1-11	1-12	1-13	1-14	1-15	1-16	1-17	1-18	1-19	1-20
DDRAM address	0A	0B	0C	0D	0E	0F	10	11	12	13
Display position	3-1	3-2	3-3	3-4	3-5	3-6	3-7	3-8	3-9	3-10
DDRAM address	14	15	16	17	18	19	1A	1B	1C	1D
Display position	3-11	3-12	3-13	3-14	3-15	3-16	3-17	3-18	3-19	3-20
DDRAM address	1E	1F	20	21	22	23	24	25	26	27
Display position	2-1	2-2	2-3	2-4	2-5	2-6	2-7	2-8	2-9	2-10
DDRAM address	40	41	42	43	44	45	46	47	48	49
Display position	2-11	2-12	2-13	2-14	2-15	2-16	2-17	2-18	2-19	2-20
DDRAM address	4A	4B	4C	4D	4E	4F	50	51	52	53
Display position	4-1	4-2	4-3	4-4	4-5	4-6	4-7	4-8	4-9	4-10
DDRAM address	54	55	56	57	58	59	5A	5B	5C	5D
Display position	4-11	4-12	4-13	4-14	4-15	4-16	4-17	4-18	4-19	4-20
DDRAM address	5E	5F	60	61	62	63	64	65	66	67

1-1 means first character of line 1 on screen

11. INSTRUCTION TABLE

				Inst	ructio	on Co	de				_	Execution
Instruction	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0	Description	Time(fosc= 270kHz)
Clear Display	0	0	0	0	0	0	0	0	0	1	Write 20H to DDRAM set DDRAM address to 00H from AC	1.52ms
Return Home	0	0	0	0	0	0	0	0	1	-	Set DDRAM address to 00H from AC and return cursor to its original position if shifted. The contents of DDRAM are not changed.	1.52ms
Entry Mode Set	0	0	0	0	0	0	0	1	I/D	SH	Assign cursor moving direction and enable the shift of entire display	38µs
Display ON/OFF Control	0	0	0	0	0	0	1	D	С	В	Set display(D) cursor(C) and blinking of cursor(B) on/off	38µs
Cursor or Display Shift	0	0	0	0	0	1	S/C	R/L	-	-	Set cursor moving and display shift control bit, and the direction, without changing DDRAM data	38µs
Function Set	0	0	0	0	1	DL	N	F	-	-	Set interface data length(DL:8bit/4bit), number of display line (N:2line/1line) and,display font type F:5X11dots / 5X8dots	38µs
Set CGRAM Address	0	0	0	1	AC5	AC4	AC3	AC2	AC1	AC0	Set CGRAM address in address counter	38µs
Set DDRAM Address	0	0	1	AC6	AC5	AC4	AC3	AC2	AC1	AC0	Set DDRAM address in address counter	38µs
Read Busy Flag and Address	0	1	BF	AC6	AC5	AC4	AC3	AC2	AC1	AC0	Whether during internal operation or not can be known by reading BF The contents of address counter can also be read	0 µs
Write Data to RAM	1	0	D7	D6	D5	D4	D3	D2	D1	D0	Write data into internal RAM (DDRAM/CGRAM)	38µs
Read data from RAM	1	1	D7	D6	D5	D4	D3	D2	D1	D0	Read data from internal RAM (DDRAM/CGRAM)	38µs

12. INSTRUCTION DESCRIPTION

A. Clear Display

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	0	0	0	1

Clear all the display data by writing 20H (space code) to all DDRAM address, and set DDRAM address to 00H into AC (address counter).

Return cursor to the original status, namely, bring the cursor to the left edge on the first line of the display.

Make the entry mode increment (I/D = HIGH)

B. Return Home

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	0	0	1	-

Set DDRAM address to 00H into the address counter.

Return cursor to its original site and return display to its original status, if shifted. Contents of DDRAM does not change.

C. Entry Mode Set

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	0	1	I/D	SH

Set the moving direction of cursor and display.

I/D:Increment /decrement of DDRAM address(cursor or blink)

I/D=High,cursor/blink moves to right and DDRAM address is increased by 1.

I/D=low,cursor/blink moves to left and DDRAM address is decreased by 1.

*CGRAM operates the same way as DDRAM, when reading from or writing to CGRAM. **SH:Shift of entire display**

When DDRAM read (CGRAM read/write) operation or SH=Low,shifting of entire display is not performed.if SH=High, and DDRAM write operation,shift of entire display is performed according to I/D value(I/D=High,shift left, I/D=Low, shift right).

D. Display ON/OFF Control

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	1	D	С	В

D:Display ON/OFF control bit

When D=High, entire display is turned on.

When D=Low, display is turned off, but display data remains in DDRAM.

C:Cursor ON/OFF control bit

When C=High, cursor is turned on.

When C=Low, cursor is disappeared in current display ,but I/D register preserves its data.

B:Cursor Blink ON/OFF control bit

When B=High, cursor blink is on, which performs alternately between all the High data and display characters at the cursor position.

When B=Low ,blink is off.

E. Cursor or Display Shift

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	1	S/C	R/L	-	-

Shifting of right/left cursor position or display without writing or reading of display data. This instruction is used to correct or search display data.

During 2-line mode display, cursor moves to the 2nd line after the 40th digit of the 1st line. Note that display shift is performed simultaneously in all the lines.

When displayed data is shifted repeatedly, each line is shifted individually.

When display shift is performed, the contents of the address counter are not changed.

S/C	R/L	Operation
0	0	Shift cursor to the left, AC is decreased by 1
0	1	Shift cursor to the right, AC is increased by 1
1	0	Shift all the display to the left,cursor moves according to the display
1	1	Shift all the display to the right,cursor moves according to the display

FORDATA ELECTRONIC CO.,LTD
PROFESSIONAL LCD SUPPLIER FROM CHINAPRODUCT
SPEC.MODE NO.
FDCC2004C-FLYYBW-51LRPAGE13/20

F. Function set

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	1	DL	N	F	-	-

DL:Interface data length control bit

When DL=High, it means 8-bit bus mode with MPU.

When DL=Low, it means 4-bit bus mode with MPU.

When 4-bit bus mode, it needs to transfer 4-bit data twice.

N:Display line number control bit

When N=Low, 1-line display mode is set.

When N=High, 2-line display mode is set.

F:Display font type control bit

When F=Low, 5x8 dots format display mode is set. When F=High, 5x11 dots format display mode.

G. Set CGRAM Address

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	1	AC5	AC4	AC3	AC2	AC1	AC0

Set CGRAM address to AC.

This instruction makes CGRAM data available from MPU.

H. Set DDRAM Address

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	1	AC6	AC5	AC4	AC3	AC2	AC1	AC0

Set DDRAM address to AC.

This instruction makes DDRAM data available from MPU.

When 1-line display mode (N=Low), DDRAM address is from 00H to 4FH In 2-line display mode(N=High), DDRAM address in the 1^{st} line is from 00H to 27H and DDRAM address in the 2^{nd} line is from 40H to 67H

FORDATA ELECTRONIC CO.,LTD PROFESSIONAL LCD SUPPLIER FROM CHINA PRODUCT SPEC. MODE NO. PAGE 14/20

I. Read Busy Flag & Address

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	1	BF	AC6	AC5	AC4	AC3	AC2	AC1	AC0

This instruction shows whether IC is in internal operation or not .

If BF is High, internal operation is in progress and shall wait until BF is to be Low, which by then the next instruction can be performed. In this instruction you and also read the value of the address counter.

J. Write data to RAM

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
1	0	D7	D6	D5	D4	D3	D2	D1	D0

Write binary 8-bit data to DDRAM/CGRAM.

The selection of RAM from DDRAM, and CGRAM, is set by the previous address set instruction(DDRAM address set, CGRAM address set).

RAM set instruction can also determine the AC direction to RAM.

After write operation, the address is automatically increased /decreased by 1,according the entry mode.

K. Read data from RAM

ſ	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
	1	1	D7	D6	D5	D4	D3	D2	D1	D0

Read binary 8-bit data from DDRAM/CGRAM.

The selection of RAM is set by the previous address set instruction. If the address set instruction of RAM is not performed before this instruction, the data that has been read first is invalid, as the direction of AC is not yet determined. If RAM data is read several times without RAM address instructions set before read operation, the correct RAM data can be obtained from the second. But the first data would be incorrect, as there is no time margin to transfer RAM data.

FORDATA ELECTRONIC CO.,LTD	PRODUCT	MODE NO.	PAGE	45/20
PROFESSIONAL LCD SUPPLIER FROM CHINA	SPEC.	FDCC2004C-FLYYBW-51LR		15/20

In case of DDRAM read operation, cursor shift instruction plays the same role as DDRAM address set instruction, it also transfers RAM data to output data register.

After read operation, address counter is automatically increased/decreased by 1 according to the entry mode.

After CGRAM read operation, display shift may not be executed correctly.

Note:In case of RAM write operation,AC is increased/decreased by 1 as in read operation. At this time,AC indicates the next address position, but only the previous data can be read by the read instruction.

13. RELATIONSHIP BETWEEN CHARACTER CODE AND CGRAM

	С	har	act	er	cod	le		С	GR	AM	Ado	dre	SS			CG	RAI	M D	ata			Pattern
D7	D6	D5	D4	D3	D2	D1	D0	A5	A4	A3	A2	A1	A0	P7	P6	P5	P4	P3	P2	P1	P0	number
0	0	0	0	Х	0	0	0	0	0	0	0	0	0	Х	Х	Х	0	1	1	1	0	pattern 1
											0	0	1	х	Х	x	1	0	0	0	1	-
											0	1	0	х	Х	x	1	0	0	0	1	
											0	1	1	х	Х	x	1	1	1	1	1	
											1	0	0	х	Х	х	1	0	0	0	1	
											1	0	1	х	Х	х	1	0	0	0	1	
											1	1	0	х	Х	х	1	0	0	0	1	
											1	1	1	х	Х	Х	0	0	0	0	0	
0	0	0	0	х	1	1	1	0	0	0	0	0	0	x	Х	х	1	0	0	0	1	pattern8
	0	0	0	^	I	I	I	0	0	0	0	0	1	x	x	x	1	0	0	0	1	patterno
											0	1	0	x	x	x	1	0	0	0	1	
											0	1	1		x	x	1	1	1	1	1	
											1	0	-	X			1	0	0	0	1	
											1	0	0 1	X	X	X	1	0	0	0	1	
											1	1	-	X	X	X	1	0			1	
											1	1	0 1	X	X	X	0	0	0	0	0	
											I	I	I	Х	Х	Х	U	U	U	U	U	


14. DISPLAY DATA RAM(DDRAM)

DDRAM stores display data of maximum 80x8 bits(80 characters). DDRAM address is set in the address counter(AC) as a hexadecimal number

MSB						LSB
AC6	AC5	AC4	AC3	AC2	AC1	AC0

								B	оок	BIN	DING ARE	A Contraction of the second se		
	7 F	OR	DAT	TA E		CTR	ON	IC C	:0.,	LTD	PRODUCT	MODE NO.	DACE	4 6 10 0
יך										HINA	SPEC.	FDCC2004C-FLYYBW-51LR	PAGE	16/20
			ZATI		e mo	ode	(Con	diti	on: f	osc	= 270KHZ)			
					Pow	ver On								
						e > 15 ld > 4.5]			(Wait tin After V	me > 40 ms) dd > 2.7V		
	RS 0	R/W 0	DB7 0	DB6 0	DB5 1	DB4 1	DB3 X	DB2 X	DB1 X	DB0 X		not be checked before this in on set (Interface is 8 bits leng		
			[Wa	ait time	e > 4.1	ms]						
F	RS 0	R/W 0	DB7 0	DB6 0	DB5	DB4	DB3	DB2	DB1 X	DB0		not be checked before this in on set (Interface is 8 bits leng		
_				W	ait time	e > 100) µs]						
	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0	{ BF can	not be checked before this in	struction.	
L	0	0	0	0	1	1	X	X	X	X	BF can Function Specify	bn set (Interface is 8 bits leng be checked after the followin on set (Interface is 8 bits leng y the number of display lines ter font.)	ng instructi gth.	ons.
┝	RS	R/W	DB7	DB6		DB4	DB3	DB2	DB1	DB0		mber of display lines and cha		
┝	0	0	0	0	1	1	N 1	F 0	X 0	X 0		nnot be changed afterwards.		
┢	0	0	0	0	0	0	0	0	0	1	Display	y off		
F	0	0	0	0	0	0	0	1	I/ D	S	Display	y clear		
				Initi	alizat	tion	Ends				Entry n	node set		

					E	BOOKBINI	DING AREA	· · · · · · · · · · · · · · · · · · ·		
	FORDA	TA E	LECT	RON	JIC	CO.,LTD	PRODUCT	MODE NO.	DAGE	17/20
ייר						ROM CHINA	SPEC.	FDCC2004C-FLYYBW-51LR	PAGE	17/20
15.2	4-bit inte	erfac		•	ndit	ion: fosc :	= 270KHZ)			
			Pow	er On						
			Wait tim after Vd				(Wait time > After Vdd >	40 ms) 2.7V		
	-		/W DB7 0 0	DB6 0	DB5 1	DB4 1		be checked before this instru et (Interface is 8 bits length.		
	F		Wait time /W DB7 0 0			DB4 1		be checked before this instru et (Interface is 8 bits length.		
	Г	RS R	Wait time			DB4				
	-			0	1	1	Function se	<u>be checked before this instru</u> et (Interface is 8 bits length.)	_
	Г			DRC			Function se	checked after the following ir et (Set interface to be 4 bits I s 8 bits length.		5.
		0 0	/W DB7 0 0 0 0 0 0 0 0 0 0 0 0	DB6 0 0 F	DB5 1 1 X	DB4 0 0 X		et (Interface is 4 bits length. e number of the display lines ster font.)		
	F	0 0	D O D 1 D 0 D 0 D 0	0 0 0	0 0 0	0 0 1		er of display lines and charac t be changed afterwards.	ter	
	L	0 (0 1	0 I/D	0 S	Display off			
							Display cle			
		In	itializat	tion E	nds		Entry mode	5 361		



DB4-DB7

LCD Unit

If Interface Data Is 4-bit Long

Data transfer is accomplished through 4 bus lines

from DB4 to DB7. (while the rest of 4 bus lines from

Data transfer is completed when 4-bits of data is transferred twice.(upper 4-bits of data, then lower

R10-R13

HMCS43C

DB0 toDB3 are not used.)

4-bits of data.)

2. 192 types of alphanumeric, symbols and special characters can be displayed with the

3. Other preferred characters can be displayed by character generator (RAM).

- 5. Compact and light weight design which can easily be integrated into end products. 6. Single power supply +5V drive (except for extended temperature type).
- 7. Low power consumption.

Read/Write display data .etc.

Clear display Cursor at home On/Off cursor Blink character Shift display Shift cursor

M

R/W

If Interface Data Is 8-bits Long

Data transfer is made through all 8 bus lines from

1. Interface to an 8-bit or 4-bit MPU is available.

built - in character generator (ROM).

4. Various instructions may be programmed.

IORG RD

DB0 to DB7

Features



17. STANDARD FONT MAP

Upper 4bit Lower 4bit	LLLL	LLLH	LLHL	LLHH	LHLL	LHLH	LHHL	LHHH	HLLL	HLLH	HLHL	HLHH	HHLL	HHLH	HHHL	нннн
LLLL																
LLLH																
LLHL																
LLHH																
LHLL																
LHLH																
LHHL																
LHHH																
HLLL																
HLLH																
HLHL																
HLHH																
HHLL																
HHLH																
HHHL																
нннн																

imated for referay be changed	rence oi	
ay be changed v	without	notice
>		
<u></u>		
く		
		7
	×	
\sim		
	\geq	
\backslash	\geq	۲
>		
\sim		