

Merchandising/Packaging	2
Drilling	4
Drilling Systems	6
Drill Bit Selection	7
Masonry Drill Bits	11
EXTREME DeWALT® Masonry Drill Bits	12
Multi-Material Drill Bits	12
SDS-Plus EXTREME DeWALT® 2 Drill Bits	13
EXTREME DeWALT® XLR Full Head Carbide Drill Bits	16
EXTREME DeWALT® Full Head Carbide Drill Bit Sets	17
SDS-Plus 4-Cutter Drill Bits	17
SDS-Max Hammer Drill Bits	18
Chisels	19
SDS Chisels	20
Pavement Breaker Drills	22
Light Duty SDS-Plus Core Drills	22
Heavy Duty SDS-Max Core Drills	22
Light & Heavy Duty Core Adapters	23
Single Piece Cores	23
Through Drilling Bits	23
Drive Adapters & Adapter - SDS-Plus	23
Metal Drilling	24
Stationary Hard Material Drill Bits	25
HSS-CO EXTREME DeWALT® Cobalt Metal Drill Bits	26
EXTREME DeWALT® 2 Metal Drill Bits	28
HSS-G DIN 338 Jobber Metal Drill Bits	30
HSS-G DIN 340 Long Series Metal Drill Bits	33
Step Drills	34
Impact Driver Drill Bits	34
Wood Drilling	35
Brad Point Wood Drill Bits	36
Frame Drill Bits	36
TCT Hinge Boring Bits	36
Wood Auger Drill Bits	37
Self Feed Drill Bits	37
Flatwood Drill Bits	38
EXTREME DeWALT® Flat Wood Drill Bits	39
EXTREME DeWALT® 406mm Flat Wood Drill Bits	39
Holesaws	40
Bi-Metal Deep Cut Holesaws	41
Holesaw Mandrels and Accessories	42
Bi-Metal Holesaw Sets	42
Quick Change Mandrels and Accessories	43
Carbide Grit Holesaws	43
Holesaw Mandrels and Accessories	44
Carbide Grit Holesaw Sets	44
Drilling Accessories	44
Mixer Tools	44
Chucks & Keys	45
Screwdriving	46
Screwdriving Accessories	48
DeWALT 'Flip & Drive' Units	53
Pilot Bits	53
Countersink & Pilot	53
Drilling Sets	54
Screwdriving Sets	56
Tough Case Storage	57
Circular Saw Blades	60
EXTREME DeWALT® Stationary Circular Saw Blades	62
Portable Circular Saw Blades	70
EXTREME DeWALT® Portable Circular Saw Blades	74
Cordless Circular Saw Blades	78
Insert Rings	78
Circular Saw Blade Guide	80
Router Bits	82
Jigsaw Blades	98
XPC Wood Cutting Blades	100
Wood Cutting Blades T-Shank	103
Wood Cutting Blades U-Shank	105
Metal Cutting Blades T-Shank	106
EXTREME DeWALT® Bi-Metal Cutting Blades T-Shank	107
Metal Cutting Blades U-Shank	107
Wood & Metal Cutting Blades T-Shank	108
EXTREME DeWALT® Special Material Blades T-Shank	108
Wood & Metal Cutting Blade Kits T-Shank	109
Reciprocating Saw Blades	110
Wood Cutting Blades Bi-Metal	112
Wood Cutting Blades HCS	113
Metal Cutting Blades Bi-Metal	114
General Purpose Blades Bi-Metal	115
Demolition Blades	116
Specialist Blades	117
Reciprocating Blade Sets	119
ALLIGATOR® Saw Blades	119
Bandsaw Blades	120
Planer Blades & Jointer Accessories	121
Coated Abrasives	122
Full Sheet	124
Half Sheet	125
Third Sheet	126
Quarter Sheet	128
Detail	128
Rolls & Belts	129
Grinding Belts	131
Nylon Loop Discs	132
Extreme Fibre Discs	133
DeWALT® Flap Discs	134
Honing Belts	134
Pads & Bonnets	135
'Quick Fit' Platens	135
Angle Grinder Polishing Bonnets	135
Bonded Abrasives	136
Metal Cutting and Grinding Discs	137
Chop Saw Wheel	137
High Speed Metal Cutting Discs	138
Stainless Steel & Thin Metal Cutting Discs	138
Aluminium Cutting Discs	138
High Speed Stone Cutting Discs	139
Stone Cutting and Grinding Discs	139
Grinding Wheels & Honing Wheels	139
Wire Brushes	140
Diamond Discs	141
Laser Blades	144
Dry Diamond Discs	147
Wet Diamond Tile Saw	148
Diamond Drills	149
Dry Diamond Core Drills & Dosenenker	150
Wet Diamond Core Bits	151
Adapters, Extension Rods & Pilot Bits	152
Diamond Tile Drill Bits	153
Nailer Accessories	154
Nails	155
Staples	156

IN STORE MERCHANDISING AND DISPLAY SYSTEM



- FLEXIBLE, MODULAR SYSTEM
- CLEAR PRODUCT DIFFERENTIATION AND COMMUNICATION
- STRONG DEWALT BRANDING

POINT-OF-SALE STRIPS



PROFESSIONAL PACKAGING

- STRONG ROBUST PACKAGING FITS INDUSTRIAL USER'S REQUIREMENTS
- ON PACK COMMUNICATION WITH ICONS - CLEAR AND SIMPLE
- CLEAR DIFFERENTIATION BETWEEN STANDARD AND "EXTREME DEWALT" PRODUCT
- PRODUCT STORAGE



ENVIRONMENTAL

DeWALT recognises and respects the balance between industry and a healthy and sustainable environment. Our role in this balance is to manufacture our products in a way that preserves the quality of our environment for ourselves and our children, while providing employees with clean and safe working conditions.

We are committed to striving for excellence in environment, health and safety management through process improvements, advanced manufacturing techniques and pollution control practices. We expect our managers and employees to maintain our facilities at the highest standards, minimise waste generation, re-use and recycle materials and products where possible and comply with all applicable laws and regulations.

DeWALT is constantly striving to maintain the highest quality of its products by implementing rigorous product development and manufacturing controls such as Six Sigma and ISO certification.

All measurements are in mm unless otherwise stated.
DeWALT reserves the right to revise product specifications at any time without notice.
Prices are correct as of going to print. However, DeWALT reserves the right to change these,
be it a price increase or decrease.

Symbols



All products shown are in compliance with the appropriate European regulations.

DEWALT DRILLING SYSTEMS

DeWALT is a market-leading manufacturer of high performance power tools and accessories that provide a fully integrated drilling system for masonry, metal and wood. Its dedicated accessories factory in Germany was established in 1959 and now employs over 200 people, producing more than 50 million drill bits every year.

MANUFACTURING

To ensure maximum performance and customer satisfaction, DeWALT drill bits undergo the most rigorous manufacturing and testing procedures (including computer controlled milling) and the most advanced production and quality management processes. DeWALT not only produces its own bits, it even designs the machines that make them.

COMING IN 2009**FULL HEAD CARBIDE**

In 2009, DeWALT launches its most advanced SDS+ drill bit to date. Designed to perform in the hardest applications with today's new generation of harder hitting, more powerful hammers, the new DeWALT XLR Full Head Carbide drill bits offer the ultimate in drill bit durability and life. Available in diameters from 5mm to 12mm and lengths of 100mm up to 460mm the new DeWALT XLR Full Head Carbide SDS+ drill bit range covers all major fixing applications.

PRODUCT DEVELOPMENT

By talking continuously to its customers, DeWALT has gained a comprehensive knowledge of user needs and applications. Its world-class development facility utilises the latest Catia CAD system and automated test equipment to develop and test all drill bits prior to and during manufacture.

QUALITY CONTROL

DeWALT is a long-standing member of PRUF GEMEINSCHAFT MAUERBOHRER (PGM), an internationally recognised organisation that verifies the suitability of drill bits for use in anchor fixing. All drill bits are certified to the latest ISO 9001: 2000 quality standards and high technology testing machinery is used for the control of variables.

MASONRY AND CONCRETE DRILLING**MASONRY BITS**

For rotary/percussion drilling in masonry, brick/block work, natural stone, tiles, light concrete. Usage as for masonry bits.

EXTREME DEWALT® MASONRY BITS

EXTREME DEWALT® MASONRY
For rotary/percussion drilling in masonry, brick/block work, natural stone. For anchors, plastic plugs, fixings and pipework clearance.

SDS-PLUS EXTREME DEWALT® 2 HAMMER BITS

High performance long-life SDS-Plus hammer bit. Suitable for masonry, stone and concrete.

**SDS-PLUS EXTREME DEWALT® XLR FULL HEAD CARBIDE**

The ultimate in SDS Plus life and durability, designed for users with the hardest applications in masonry, stone and granite.

**SDS-PLUS 4-CUTTER BITS**

For fixing holes and through holes 16mm - 30mm.

**SDS-MAX HAMMER BITS**

For SDS-Max drive hammer drills. Suitable for masonry, stone and concrete.

**CHISELS**


For electro-pneumatic chiselling machines. Applications include demolition, channelling, surface preparation in masonry, stone, concrete, brick/block work.

CORE DRILLS (TCT)


For clean, round rotary drilling in light concrete, brick/block work. Available for SDS+ & SDS Max systems.

SDS-PLUS

The range of SDS+ Extreme Masonry drill bits possesses some important New design features which deliver the very best in DURABILITY and RELIABILITY as well as consistent performance in terms of bit life and drilling speed.

**SDS-MAX**

DeWALT's comprehensive range includes the EXTREME DeWALT® SDS-MAX hammer bits, which deliver a class leading combination of drilling speed and durability through features such as a four flute spiral with maximised entry to all flutes and a low friction head design.

**SUITABLE FOR MASONRY CONCRETE, BRICK OR BLOCK WORK**

Concrete

Brick

Block

① Manufactured in our own plant in Germany using only the best European Steel and advanced manufacturing techniques



② 4 FLUTE SPIRAL 4 separate channels on the flute give the optimum debris removal without compromising on drill bit durability, even in use with the hardest hitting hammers

**INNOVATIVE BONDING SYSTEM**



The tip and the flute are bonded as one to offer the highest standards available in SDS+ drill bit durability




48

DRILLING SYSTEMS**SDS-PLUS SYSTEM****SDS-MAX SYSTEM****19MM HEX SYSTEM****28MM HEX SYSTEM****SHANK FITMENTS****For use with**



- DeWALT: DC212N, DC212KA, DC213KA, DC213KB, DC22KA, DC222KB, DC223KA, DC224KA, DC224KB, DC234KL, DC232KL, D25112K, D25113K, D25114K, D25213K, D25313K, D25314K, D25315K, D25404K, D25405K, D25330K, DC228/229KL
- Atlas Copco: PFH 200E, PHE20R, PHE20RL-N, PHE20L, RL-N2, PHE20RL-MF2, PHE24R, PHE24R, PHE26R, PHE26RA, PHERX2, PHE26, PHF24
- Bosch: GBH 2-18, GBH 2-22RE, GBH 2-26RE, GBH 2-26DRE, GBH 2-26DFR, GAH 500DSR, GBH 24V, GBH 24VRE, GBH 24VFR, GBH 3-28E, GBH 3-28FE, GSH 3E, GBH 4DFE, GBH 4DSC
- Hilti: TE2, TE2-S, TE2-M, TE2-A, TE6-S, TE6-C, TE6-A, TE7-A, TE7-C, TE7-S, TE16, TE16-C, TE16-M, TE35C, TE104
- Hitachi: DH24DV, DH24PB3, DH24PC3, DH25PB, DH30PC, H25PV
- Kango: 285, 200, 426, 430D
- Makita: HK0500, HR2010, HR2020, HR2410, HR2420, HR2430, HR2431, HR2432, HR2440, HR2440F, HR2445, HR2450, HR2450T, HR2450F, HR2450FT, HR2455, HR2510, HR3000C, HR1830, BHR200WAE, BHR200SAJ, BHR200JE
- Metabo: UBH2/20RLE, PB E501/2S-R+L PBE701/2 SR+L Signal, BHE6010 S-E+L, BHE6012 S-R+L, BHE6020 S-R+L, BHE6026 S-R+L Signal, UHE 22 Multi, UHE 28 Multi, BHE 20 SR, BHE 6009 S, BHE6011, S-R+L, BHE 6015 S-R+L, BHE 24 SR, BHE 6021 S-R+L, BHE6024 S-R+L, BHE6028 S-R+L, KHE 32
- DeWALT: D25500K, D25600K, D25830K, D25700K, D25701K, D25840K, D25730K, D25900K, D25899K, D25901K
- Atlas Copco: PH5S, PHE 7 S, PHE50S
- Bosch: GBH 5-38 DE, GBH 5-40 DE, GBH 7-46 DE, GBH 11 DE, GSH 5E, GSH 11 E, GSH 500
- Hilti: TE56, TE56-ATC, TE76P, TE76P-ATC, TE505

**19mm Hexagon shank**

- DeWALT: D25940K, D25941K
- Atlas Copco: PB14D
- Kango: 637, 638
- Makita: HM1200B

**28mm Hexagon shank**

- DeWALT: D25980, D25980K
- Bosch: GSH27
- Makita: HM1304B
- Hitachi: H70SD

**DRILL BIT SELECTION**

DRILLING

STEP 1

Select the correct bit, material group, surface speed and coolant for your application from table 1.

STEP 2

From table 2 select the correct feed rate for the material group and bit diameter.

STEP 3

Use table 3 to convert surface speed to RPM.

STEP 4

Carry-out the application using the correct bit, RPM, feed rate & coolant.

DRILL BIT SELECTION

Table 1/Material Groups

Material Group	Material Description	Recommended Bit Selection	Point Angle	Cutting Speed	Coolant
Cold Worked Steel					
4	Non Alloyed steel up to 600N/mm ²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	30-40	Emulsion
4	Non Alloyed steel up to 600-800N/mm ²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	25-35	Emulsion
4	Steel sheet up to 800N/mm ²	EXTREME DeWALT® 2 Metal	Split point	-	Emulsion
4	Non Alloyed Tool Sheet upto 800N/mm ²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	20-30	Emulsion
4	Alloyed Tool sheet 700-800N/mm ²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	10-15	Emulsion
3	Alloyed Tool Sheet 800-1000N/mm ²	HSS-R/HSS-G/			
		HSS-CO EXTREME DeWALT® Cobalt	118°/130°	8-12	Oil
2	Alloyed Tool Sheet 1000-1200N/mm ²	HSS-CO EXTREME DeWALT® Cobalt	130°	6-10	Oil
1	Spring Steel	HSS-CO EXTREME DeWALT® Cobalt	130°	5-10	Oil
3	Stainless Steel (Austenitic) 500-800N/mm ²	HSS-CO EXTREME DeWALT® Cobalt	130°	5-10	Oil
2	Heat Resistant Steel up to 800N/mm ²	HSS-CO EXTREME DeWALT® Cobalt	130°	5-15	Oil
5	Cast Iron up to 250N/mm ²	HSS-G/HSS-CO EXTREME DeWALT® Cobalt	118°/130°	15-25	Emulsion/Air
Non Ferrous Metal					
5	Copper Non Alloyed	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	30-40	Emulsion
5	Copper Alloyed	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	25-35	Emulsion
6	Aluminium Alloyed & Non alloyed	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	40-100	Emulsion
6	Cast Aluminium	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	40-65	Emulsion
3	Titanium & Titanium Alloys	HSS-CO EXTREME DeWALT® Cobalt	130°	3-60	Oil
5	Brass (long chippings)	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	30-40	Emulsion
6	Brass (short chippings)	EXTREME DeWALT® 2 Metal	Split point	40-60	Emulsion
4	Bronze	HSS-G/HSS-CO EXTREME DeWALT® Cobalt/ EXTREME DeWALT® 2 Metal	118°/Split point	25-35	Emulsion
5	Aluminium, Copper, Brass sheet	EXTREME DeWALT® 2 Metal	Split point	-	Emulsion
6	Magnesium & Mrg. Alloys	EXTREME DeWALT® 2 Metal	Split point	60-100	Emulsion
Plastic/Synthetic Material					
6	Thermoplastic- PVC, Plexiglass, Polymide	HSS-R/HSS-G/ EXTREME DeWALT® 2 Metal	118°/Split point	20-40	Air
4	Duroplastic, Bakelite, Hard rubber	HSS-R/HSS-G/ EXTREME DeWALT® 2 Metal	118°/Split point	15-20	Air
Stone/Masonry					
	Red brick, Gabstein, Ziegel	All Conc/Masonry bits	130°/EXTREME DeWALT® Tip -		Air
	Hard Brick, Klinker, Sandlime block	All Conc/Masonry bits	130°/EXTREME DeWALT® Tip -		Air
	Light Concrete	All Conc/Masonry drill bits	130°/EXTREME DeWALT® Tip -		Air
	Hard/Reinforced Concrete	SDS-Plus EXTREME DeWALT® 2/SDS-Plus	130°/EXTREME DeWALT® Tip -		Air
	Natural Stone (Granite/Marble)	EXTREME DeWALT® Masonry/ SDS-Plus EXTREME DeWALT® 2	EXTREME DeWALT® Tip	*	Air
	Slate	EXTREME DeWALT® Masonry	EXTREME DeWALT® Tip	*	Air
	Wall Tiles (Soft Ceramic)	EXTREME DeWALT® Masonry	EXTREME DeWALT® Tip	*	Air
	Floor Tiles (Hard Ceramic)	EXTREME DeWALT® Masonry/ SDS-Plus EXTREME DeWALT® 2	EXTREME DeWALT® Tip	*	Air

* Low RPM without percussion or hammer action when drilling tiles

Table 2 / Recommended Feed Rates

Feedrate (mm/REV) by bit diameter & Material Group																
Material Group	Ø 1	Ø 2	Ø 2.5	Ø 3	Ø 4	Ø 5	Ø 6	Ø 8	Ø 10	Ø 12	Ø 16	Ø 20	Ø 25	Ø 30	Ø 40	Ø 50
1	0.004	0.02	0.02	0.03	0.04	0.05	0.05	0.06	0.08	0.1	0.12	0.12	0.16	0.2	0.2	0.25
2	0.006	0.02	0.03	0.04	0.05	0.05	0.06	0.08	0.1	0.12	0.16	0.16	0.2	0.25	0.25	0.3
3	0.008	0.03	0.04	0.05	0.06	0.06	0.08	0.1	0.12	0.13	0.2	0.2	0.25	0.3	0.3	0.4
4	0.01	0.04	0.05	0.06	0.08	0.1	0.1	0.12	0.16	0.2	0.25	0.25	0.3	0.4	0.4	0.5
5	0.01	0.05	0.06	0.08	0.1	0.1	0.12	0.16	0.2	0.25	0.3	0.3	0.4	0.5	0.5	0.6
6	0.012	0.06	0.08	0.1	0.12	0.12	0.16	0.2	0.25	0.25	0.4	0.4	0.5	0.6	0.6	0.8

Table 3/Recommended Surface Speed and RPM

Surface speed m/min

Ø mm	4	6	8	10	12	15	18	20	25	30	35	40	50
1	1273	1909	2545	3182	3818	4773	5727	6364	7955	9545	11136	12727	15909
1.5	848	1273	1607	2121	2545	3182	3818	4242	5303	6364	7424	8485	10606
2	636	955	1273	1591	1909	2386	3182	3977	4773	5568	6364	7955	
2.5	509	764	1018	1273	1527	1909	2291	2545	3182	3818	4455	5091	6364
3	424	636	848	1061	1273	1591	1909	2121	2652	3182	3712	4242	5303
3.5	364	545	727	909	1091	1364	1636	1818	2273	2727	3182	3636	4545
4	318	477	636	795	955	1193	1432	1591	1989	2386	2784	3182	3977
4.5	283	424	566	707	848	1061	1273	1414	1768	2121	2475	2828	3535
5	255	382	509	636	764	955	1145	1273	1591	1909	2227	2545	3182
5.5	231	347	463	579	694	868	1041	1157	1446	1736	2025	2314	2893
6	212	318	424	530	636	795	955	1061	1326	1591	1856	2121	2652
6.5	196	294	392	490	587	734	881	979	1224	1469	1713	1958	2448
7	182	273	364	455	545	682	818	909	1136	1364	1591	1818	2273
7.5	170	255	339	424	509	636	764	848	1061	1273	1485	1697	2121
8	159	239	318	398	477	597	716	795	994	1193	1392	1591	1989
8.5	150	225	299	374	449	561	674	749	936	1123	1310	1497	1872
9	141	212	283	354	424	530	636	707	884	1061	1237	1414	1768
9.5	134	201	268	335	402	502	603	670	837	1005	1172	1340	1675
10	127	191	255	318	382	477	573	636	795	955	1114	1273	1591
11	116	174	231	289	347	434	521	579	723	868	1012	1157	1446
12	106	159	212	265	318	398	477	530	663	795	928	1061	1326
13	98	147	196	245	294	367	441	490	612	734	857	979	1224
14	91	136	182	227	273	341	409	455	568	682	795	909	1136
15	85	127	170	212	255	318	382	424	530	636	742	848	1061
16	80	119	159	199	239	298	358	398	497	597	696	795	994
17	75	112	150	187	225	281	337	374	468	561	655	749	936
18	71	106	141	177	212	265	318	354	442	530	619	707	884
19	67	100	134	167	201	251	301	335	419	502	586	670	837
20	64	95	127	159	191	239	286	318	398	477	557	636	795
21	61	91	121	152	182	227	273	303	379	455	530	606	758
22	58	87	116	145	174	217	260	289	362	434	506	579	723
23	55	83	111	138	166	208	249	277	346	415	484	553	692
24	53	80	106	133	159	199	239	265	331	398	464	530	663
25	51	76	102	127	153	191	229	255	318	382	445	509	636
26	49	73	98	122	147	184	220	245	306	367	428	490	612
27	47	71	94	118	141	177	212	236	295	354	412	471	589
28	45	68	91	114	136	170	205	227	284	341	398	455	568
29	44	66	88	110	132	165	197	219	274	329	384	439	549
30	42	64	85	106	127	159	191	212	265	318	371	424	530
31	41	62	82	103	123	154	185	205	257	308	359	411	513
32	40	60	80	99	119	1							

USEFUL DRILL BIT SIZES**Metric Coarse DIN 13**

Size	Thread Pitch	Tap Drill Dia
1,0	0.25	0.75
1,1	0.25	0.85
1,2	0.25	0.95
1,4	0.30	1.10
1,6	0.35	1.25
1,8	0.35	1.45
2,0	0.40	1.60
2,2	0.45	1.75
2,5	0.45	2.05
3,0	0.50	2.50
3,5	0.60	2.90
4,0	0.70	3.30
4,5	0.75	3.70
5,0	0.80	4.20
6,0	1.00	5.00
7,0	1.00	6.00
8,0	1.25	6.80
9,0	1.25	7.80
10,0	1.50	8.50
11,0	1.50	9.50
12,0	1.75	10.20
14,0	2.00	12.00
16,0	2.00	14.00
18,0	2.50	15.50
20,0	2.50	17.50
22,0	2.50	19.50
24,0	3.00	21.00
27,0	3.00	24.00
30,0	3.50	26.50
33,0	3.50	29.50
36,0	4.00	32.00
39,0	4.00	35.00
42,0	4.40	37.50
45,0	4.40	40.50
48,0	5.00	43.00
52,0	5.00	47.00
56,0	5.50	50.50
60,0	5.50	54.50
64,0	6.00	58.00
68,0	6.00	62.00

Metric Fine DIN 13

Size	Tap Drill Dia
10 x 0,50	9.50
10 x 0,75	9.20
10 x 1,00	9.00
10 x 1,25	8.80
11 x 1,00	10.00
12 x 0,75	11.20
12 x 1,00	11.00
12 x 1,25	10.80
12 x 1,50	10.50
13 x 1,00	12.00
14 x 1,00	13.00
14 x 1,80	12.80
14 x 1,50	12.50
15 x 1,00	14.00
15 x 1,50	13.50
16 x 1,00	15.00
16 x 1,50	14.50
18 x 1,00	17.00
18 x 1,50	16.50
18 x 2,00	16.00
20 x 1,00	19.00
20 x 1,50	18.50
20 x 2,00	18.00
22 x 1,00	21.00
22 x 1,50	20.50
22 x 2,00	20.00
24 x 1,00	23.00
24 x 1,50	22.50
24 x 2,00	22.00
25 x 1,00	24.00
25 x 1,50	23.50
26 x 1,50	24.50
27 x 1,50	25.50
27 x 2,00	25.00
28 x 1,50	26.50
28 x 2,00	26.00
30 x 1,00	29.00
30 x 1,50	28.50
30 x 2,00	28.00
32 x 1,50	30.50
33 x 1,50	31.50
33 x 2,00	31.00
34 x 1,50	32.30
35 x 1,50	33.40
36 x 1,50	34.40
36 x 2,00	34.00
36 x 3,00	33.00
38 x 1,50	36.50
39 x 1,50	37.50
39 x 2,00	37.00
39 x 3,00	36.00
40 x 1,50	38.50
40 x 2,00	38.00
40 x 3,00	37.00
42 x 1,50	40.40
42 x 2,00	40.00
42 x 3,00	39.00
45 x 1,50	43.40
45 x 2,00	43.00
45 x 3,00	42.00
48 x 1,50	46.50
48 x 2,00	46.00

Metric Fine DIN 13


Size	Tap Drill Dia
2,0 x 0,25	1.75
2,2 x 0,25	1.95
2,3 x 0,25	2.05
2,5 x 0,35	2.15
2,6 x 0,35	2.20
3,0 x 0,35	2.65
3,5 x 0,35	3.15
4,0 x 0,35	3.65
4,0 x 0,50	3.50
5,0 x 0,50	4.50
6,0 x 0,50	5.50
6,0 x 0,75	5.20
7,0 x 0,75	6.20
8,0 x 0,50	7.50
8,0 x 0,75	7.20
8,0 x 1,00	7.00
9,0 x 0,75	8.20
9,0 x 1,00	8.00

Metric Fine DIN 13

Size	Tap Drill Dia
48 x 3,00	45.00
50 x 1,50	48.50
50 x 2,00	48.00
50 x 3,00	47.00
52 x 1,50	50.50
52 x 2,00	50.00
52 x 3,00	49.00

Whitworth G Threads DIN ISO 228/1

Size	Thread Pitch	Tap Drill Dia
G 1/8"	28	8.80
G 1/4"	19	11.80
G 3/8"	19	15.25
G 1/2"	14	19.00
G 5/8"	14	21.00
G 3/4"	14	24.50
G 7/8"	14	28.25
G1"	11	30.75
G1 1/8"	11	35.30
G1 1/4"	11	39.25
G1 3/8"	11	41.70
G1 1/2"	11	45.25
G1 3/4"	11	51.00
G2"	11	57.00
G2 1/4"	11	63.10
G2 1/2"	11	72.60
G2 3/4"	11	78.90
G3"	11	85.30
G3 1/4"	11	91.50
G3 1/2"	11	97.70
G3 3/4"	11	104.00
G4"	11	110.40

MASONRY DRILL BITS**SINGLE PACKS**

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6500QZ	3	60	28	1	1	5011402382309	1.04
DT6504QZ	4	75	38	1	1	5011402372379	1.06
DT6501QZ	4.5	85	44	1	1	5011402372393	1.00
DT6505QZ	5	85	44	1	1	5011402372416	1.16
DT6502QZ	5.5	85	44	1	1	5011402372454	1.19
DT6552QZ	5.5	150	82	1	1	5011402372478	1.60
DT6506QZ	6	100	54	1	1	5011402372492	1.34
DT6556QZ	6	150	82	1	1	5011402372515	1.98
DT6606QZ	6	200	135	1	1	5011402372539	2.24
DT6503QZ	6.5	100	54	1	1	5011402372553	1.36
DT6603QZ	6.5	200	135	1	1	5011402372591	2.35
DT6507QZ	7	100	54	1	1	5011402372614	1.41
DT6557QZ	7	150	82	1	1	5011402372638	2.14
DT6508QZ	8	120	67	1	1	5011402372676	1.50
DT6558QZ	8	150	82	1	1	5011402372690	2.14
DT6608QZ	8	200	135	1	1	5011402372713	2.54
DT6708QZ	8	400	230	1	1	5011402372737	5.08
DT6509QZ	9	120	67	1	1	5011402372751	2.20
DT6609QZ	9	200	135	1	1	5011402372799	2.69
DT6510QZ	10	120	67	1	1	5011402372836	2.20
DT6560QZ	10	150	82	1	1	5011402372850	2.14
DT6610QZ	10	200	135	1	1	5011402372874	2.70
DT6710QZ	10	400	230	1	1	5011402372898	5.67
DT6732QZ	10	600	400	1	1	5011402382361	6.88
DT6561QZ	11	150	82	1	1	5011402372911	2.54
DT6562QZ	12	150	82	1	1	5011402372935	2.92
DT6612QZ	12	200	135	1	1	5011402372959	3.75
DT6712QZ	12	400	230	1	1	5011402372973	6.72
DT6733QZ	12	600	400	1	1	5011402382378	7.16
DT6563QZ	13	150	82	1	1	5011402372997	3.07
DT6713QZ	13	400	230	1	1	5011402373031	7.59
DT6564QZ	14	150	82	1	1	5011402373055	3.07
DT6714QZ	14	400	230	1	1	5011402373093	8.23
DT6734QZ	14	600	400	1	1	5011402382385	7.86
DT6565QZ	15	150	82	1	1	5011402373116	5.26
DT6566QZ	16	150	82	1	1	5011402373154	5.79
DT6716QZ	16	400	230	1	1	5011402373192	8.63
DT6735QZ	16	600	400	1	1	5011402382392	10.75
DT6718QZ	18	400	230	1	1	5011402373192	11.15
DT6736QZ	18	600	400	1	1	5011402382408	12.63
DT6720QZ	20	400	230	1	1	5011402373239	11.82
DT6737QZ	20	600	400	1	1	5011402382415	13.93


MASONRY DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)

<tbl_r cells="7" ix="2" maxcspan="1




**FOR USE WITH
ROTARY OR
PERCUSSION
DRILLS (Corded & Cordless)**

**APPLICATIONS**

- Typically used for drilling anchor, plastic plug, fixing or pipework clearance holes.
- Suitable for masonry, brick, stone, tiles and light concrete.

FEATURES

- Lasts up to 2x longer and delivers up to 50% more holes per charge than a standard masonry bit.
- Unique Carbide Grade - optimum grade maximises durability.

**APPLICATIONS**

- Suitable for wood, plastics, mild steel and non ferrous metals and masonry.
- For use in rotary or percussion drilling modes.

FEATURES


- Unique 120° tip grind for maximum sharpness.
- Fully supported carbide head gives faster drilling and extended life.
- Non slip shank ensures better retention in chuck.

**EXTREME DEWALT® MASONRY DRILL BITS
SINGLE PACKS**

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6695QZ	3	110	70	1	1	5035048061879	2.25
DT6699QZ	3.5	110	70	1	1	5035048014028	NOT UK
DT6696QZ	4	110	70	1	1	5035048061886	2.30
DT6671QZ	4	75	50	1	1	5035048060568	2.15
DT6672QZ	5	85	50	1	1	5035048060575	2.17
DT6673QZ	5	150	100	1	1	5035048060582	3.42
DT6674QZ	5.5	85	50	1	1	5035048060599	2.30
DT6675QZ	6	100	60	1	1	5035048060605	2.37
DT6676QZ	6	150	100	1	1	5035048060612	3.17
DT6677QZ	6	200	150	1	1	5035048060629	3.94
DT6678QZ	6.5	100	60	1	1	5035048060636	2.41
DT6679QZ	6.5	150	100	1	1	5035048060643	3.42
DT6680QZ	7	100	60	1	1	5035048060650	2.80
DT6681QZ	7	150	100	1	1	5035048060667	3.42
DT6682QZ	8	120	80	1	1	5035048060674	2.80
DT6683QZ	8	200	150	1	1	5035048060681	4.07
DT6684QZ	9	120	80	1	1	5035048060698	4.20
DT6685QZ	10	120	80	1	1	5035048060704	3.60
DT6686QZ	10	200	150	1	1	5035048060711	4.29
DT6687QZ	12	150	100	1	1	5035048060728	5.01
DT6688QZ	12	200	150	1	1	5035048060735	6.00
DT6689QZ	13	150	100	1	1	5035048060742	6.50
DT6690QZ	14	150	100	1	1	5035048060759	7.64
DT6691QZ	14	200	150	1	1	5035048060766	8.72
DT6692QZ	16	150	100	1	1	5035048060773	9.25
DT6693QZ	16	200	150	1	1	5035048060780	9.31

EXTREME DEWALT® MASONRY DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6956QZ	5 piece set in plastic cassette.	4,5,6,8,10	5	1	5035048060797	11.82
DT7928QZ	Ph2x4, P2x4, Ph2x50mm, P2x50mm, Slotted 5.5x50mm, Magnetic holder, Magnetic drive guide.	4, 5, 5.5, 6, 7, 8	19	1	5035048060803	49.48
DT7928BQZ	Blister Pack				5035048072219	49.48

MULTI MATERIAL DRILL BITS

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6515QZ	3	113	83	1	1	5035048066010	2.14
DT6516QZ	3.5	113	83	1	1	5035048066027	2.36
DT6517QZ	4	103	73	1	1	5035048066034	2.68
DT6518QZ	5	113	83	1	1	5035048066041	2.81
DT6527QZ	5.5	113	83	1	1	5035048077504	2.69
DT6528QZ	5.5	200	170	1	1	5035048077511	3.27
DT6519QZ	6	123	93	1	1	5035048066058	3.05
DT6529QZ	6	200	170	1	1	5035048077528	3.70
DT6520QZ	6.5	123	93	1	1	5035048066065	3.32
DT6530QZ	6.5	200	170	1	1	5035048077535	4.04
DT6521QZ	7	123	93	1	1	5035048066072	3.91
DT6522QZ	8	134	104	1	1	5035048066089	4.03
DT6531QZ	8	200	170	1	1	5035048077542	4.92
DT6523QZ	9	134	104	1	1	5035048066096	4.28
DT6524QZ	10	134	104	1	1	5035048066102	4.39
DT6533QZ	10	200	170	1	1	5035048077559	4.61
DT6525QZ	12	153	123	1	1	5035048066119	5.89
DT6526QZ	13	160	130	1	1	5035048066126	8.68

**SDS-PLUS EXTREME DEWALT® 2
DRILL BITS SINGLE PACKS**

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT9625QZ	3	135	75	1	1	5035048014011	NOT UK
DT9500QZ	3.5	110	50	1	1	5035048054758	5.40
DT9502QZ	4	110	50	1	1	5035048054772	3.28
DT9503QZ	4	160	100	1	1	5035048054789	5.07
DT9504QZ	5	110	50	1	1	5035048054796	2.91
DT9505QZ	5	160	100	1	1	5035048054802	3.45
DT9506QZ	5	210	150	1	1	5035048054819	5.15
DT9507QZ	5	310	250	1	1	5035048054826	8.83
DT9620QZ	5	460	400	1	1	5035048061855	18.34
DT9508QZ	5.5	110	50	1	1	5035048054833	3.01
DT9509QZ	5.5	160	100	1	1	5035048054840	3.30
DT9510QZ	5.5	210	150	1	1	5035048054857	4.84
DT9511QZ	5.5	260	200	1	1	5035048054864	6.58
DT9512QZ	5.5	310	250	1	1	5035048054871	8.95
DT9513QZ	5.5	460	400	1	1	5035048054888	20.22
DT9514QZ	6	110	50	1	1	5035048054901	3.45
DT9515QZ	6	160	100	1	1	5035048054918	4.86
DT9516QZ	6	210	150	1	1	5035048054918	4.86
DT9517QZ	6	260	200	1	1	5035048054925	7.41
DT9621QZ	6	310	250	1	1	5035048061862	8.65
DT9518QZ	6	460	400	1	1	5035048054932	19.40
DT9519QZ	6.5	110	50	1	1	5035048054949	3.18
DT9520QZ	6.5	160	100	1	1	5035048054956	3.59
DT9521QZ	6.5	210	150	1	1	5035048054963	3.82
DT9522QZ	6.5	260	200	1	1	5035048054970	8.41
DT9523QZ	6.5	310	250	1	1	5035048054987	9.53
DT9524QZ	7	110	50	1	1	5035048054994	3.49
DT9525QZ	7	160	100	1	1	5035048055007	3.75
DT9526QZ	7	210	150	1	1	5035048055014	5.65
DT9527QZ	7	260	200	1	1	5035048055021	6.19
DT9528QZ	8	110	50	1	1	5035048055038	3.50
DT9529QZ	8	160	100	1	1	5035048055045	3.89
DT9530QZ	8	210	150	1	1	5035048055052	4.53
DT9531QZ	8	260	200	1	1	5035048055069	7.41
DT9532QZ	8	310	250	1	1	5035048055076	8.94
DT9533QZ	8	410	350	1	1	5035048055083	14.15
DT9534QZ	8	460	400	1	1	5035048055090	13.00
DT9535QZ	8	600	540	1	1	5035048055106	18.94
DT9536QZ	9	160	100	1	1	5035048055113	5.03
DT9537QZ	9	210	150	1	1	5035048055120	6.66
DT9539QZ	10	110	50	1	1	5035048055144	3.62
DT9540QZ	10	160	100	1	1	5035048055151	4.25
DT9541QZ	10	210	150	1	1	5035048055168	5.09
DT9542QZ	10	260	200	1	1	5035048055175	6.87
DT9543QZ	10	310	250	1	1	5035048055182	5.79
DT9544QZ	10	350	300	1	1	5035048055199	8.00
DT9545QZ	10	460	400	1	1	5035048055205	12.31
DT9546QZ	10	600	550	1	1	5035048055212	17.11
DT9547QZ	10	1000	950	1	1	503504	



FOR USE WITH
SDS-PLUS
HAMMER DRILLS



APPLICATIONS

- Suitable for fast drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work.

FEATURES

- The innovative EXTREME DeWALT® 2 SDS+ drill bit is amongst the very best in terms of its durability drilling life and speed.
- The Superior carbide grade ensures a tip with outstanding durability which gives consistent drilling life.
- The NEW 4 FLUTE SPIRAL incorporates a maximized central core for increased durability and energy transmission.
- The 140° tip design ensures better bit penetration and longer life.
- Hardened Steel body for extra strength and reduced breakage.



SDS-PLUS EXTREME DEWALT® 2 DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT9559QZ	12	1000	950	1	1	5035048055342	44.96
DT9560QZ	13	160	100	1	1	5035048055359	6.03
DT9561QZ	13	200	150	1	1	5035048055366	6.02
DT9562QZ	13	260	200	1	1	5035048055373	7.65
DT9563QZ	13	300	250	1	1	5035048055380	8.57
DT9565QZ	13	450	400	1	1	5035048055403	11.97
DT9566QZ	14	160	100	1	1	5035048055410	7.02
DT9567QZ	14	200	150	1	1	5035048055427	7.13
DT9568QZ	14	260	200	1	1	5035048055434	7.82
DT9569QZ	14	300	250	1	1	5035048055441	9.05
DT9570QZ	14	450	400	1	1	5035048055458	13.43
DT9571QZ	14	600	550	1	1	5035048055465	19.10
DT9572QZ	14	1000	950	1	1	5035048055472	49.08
DT9573QZ	15	160	100	1	1	5035048055489	6.69
DT9574QZ	15	200	150	1	1	5035048055496	7.65
DT9575QZ	15	260	200	1	1	5035048055502	9.00
DT9576QZ	15	300	250	1	1	5035048055519	10.02
DT9577QZ	15	450	400	1	1	5035048055526	13.49
DT9578QZ	16	160	100	1	1	5035048055533	7.31
DT9579QZ	16	200	150	1	1	5035048055540	8.64
DT9580QZ	16	260	200	1	1	5035048055557	9.34
DT9581QZ	16	300	250	1	1	5035048055564	11.01
DT9582QZ	16	450	400	1	1	5035048055571	15.24
DT9583QZ	16	600	550	1	1	5035048055588	23.14
DT9584QZ	16	800	750	1	1	5035048055595	34.30
DT9585QZ	16	1000	950	1	1	5035048055601	51.19
DT9586QZ	17	200	150	1	1	5035048055618	16.18
DT9587QZ	18	200	150	1	1	5035048055625	10.66
DT9588QZ	18	250	200	1	1	5035048055632	11.81
DT9589QZ	18	300	250	1	1	5035048055649	14.84
DT9590QZ	18	450	400	1	1	5035048055656	21.37
DT9591QZ	18	600	550	1	1	5035048055663	29.01
DT9592QZ	18	800	750	1	1	5035048055670	47.48
DT9593QZ	18	1000	950	1	1	5035048055687	68.14
DT9596QZ	19	450	400	1	1	5035048055717	24.12
DT9597QZ	20	200	150	1	1	5035048055724	12.12
DT9598QZ	20	300	250	1	1	5035048055731	16.79
DT9599QZ	20	450	400	1	1	5035048055748	24.32
DT9600QZ	20	600	550	1	1	5035048055755	33.59
DT9601QZ	20	1000	950	1	1	5035048055762	76.69
DT9602QZ	22	250	200	1	1	5035048055779	18.70
DT9603QZ	22	300	250	1	1	5035048055786	20.24
DT9604QZ	22	450	400	1	1	5035048055793	26.64
DT9605QZ	22	600	550	1	1	5035048055809	33.74
DT9606QZ	22	800	750	1	1	5035048055816	52.63
DT9607QZ	22	1000	950	1	1	5035048055823	84.12
DT9608QZ	23	250	200	1	1	5035048055830	27.56
DT9609QZ	24	250	200	1	1	5035048055847	21.17
DT9610QZ	24	450	400	1	1	5035048055854	28.91
DT9611QZ	25	250	200	1	1	5035048055861	23.22
DT9612QZ	25	300	250	1	1	5035048055878	24.41
DT9613QZ	25	450	400	1	1	5035048055885	30.12
DT9614QZ	25	1000	950	1	1	5035048055892	89.34
DT9615QZ	26	250	200	1	1	5035048055908	26.75
DT9616QZ	26	450	400	1	1	5035048055915	31.85
DT9617QZ	26	800	750	1	1	5035048055922	70.33
DT9618QZ	30	250	200	1	1	5035048055939	40.54
DT9619QZ	30	450	400	1	1	5035048055946	48.07





FOR USE WITH
SDS-PLUS
HAMMER DRILLS




APPLICATIONS

- Suitable for drilling plug & anchor holes in masonry, all types of stone and concrete.

FEATURES

- New solid carbide drill tip with optimised 4 cutter geometry offers the highest levels of drill bit life and durability from DeWALT to date.
- 4 cutter geometry drills a more concentric hole to offer the best fixing retention.
- 4 flute spiral aids consistent drilling speed and efficient debris removal.
- Unique bonding system joins the solid carbide head to the 4 flute spiral as one to ensure the highest standards available in DeWALT SDS+ drilling to date.

EXTREME DeWALT® XLR FULL HEAD CARBIDE DRILL BITS SINGLE PACKS



COMING
IN
2009

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT8907QZ	5	110	50	1	1	5035048077689	TBC
DT8908QZ	5	160	100	1	1	5035048077696	TBC
DT8909QZ	5	210	150	1	1	5035048077702	TBC
DT8910QZ	5.5	110	50	1	1	5035048077719	TBC
DT8911QZ	5.5	160	100	1	1	5035048077726	TBC
DT8912QZ	6	110	50	1	1	5035048077733	TBC
DT8913QZ	6	160	100	1	1	5035048077740	TBC
DT8914QZ	6	210	150	1	1	5035048077757	TBC
DT8915QZ	6	260	200	1	1	5035048077764	TBC
DT8916QZ	6.5	160	100	1	1	5035048077771	TBC
DT8917QZ	6.5	210	150	1	1	5035048077788	TBC
DT8918QZ	6.5	260	200	1	1	5035048077795	TBC
DT8919QZ	6.5	310	250	1	1	5035048077801	TBC
DT8920QZ	7	160	100	1	1	5035048077818	TBC
DT8921QZ	7	210	150	1	1	5035048077825	TBC
DT8922QZ	8	110	50	1	1	5035048077832	TBC
DT8923QZ	8	160	100	1	1	5035048077849	TBC
DT8924QZ	8	210	150	1	1	5035048077856	TBC
DT8925QZ	8	260	200	1	1	5035048077863	TBC
DT8926QZ	8	310	250	1	1	5035048077870	TBC
DT8927QZ	8	460	400	1	1	5035048077887	TBC
DT8928QZ	10	160	100	1	1	5035048077894	TBC
DT8929QZ	10	210	150	1	1	5035048077900	TBC
DT8930QZ	10	260	200	1	1	5035048077917	TBC
DT8931QZ	10	310	250	1	1	5035048077924	TBC
DT8932QZ	10	460	400	1	1	5035048077931	TBC
DT8933QZ	12	160	100	1	1	5035048077948	TBC
DT8934QZ	12	200	150	1	1	5035048077955	TBC
DT8935QZ	12	260	200	1	1	5035048077962	TBC
DT8936QZ	12	310	260	1	1	5035048077979	TBC
DT8937QZ	12	460	410	1	1	5035048077986	TBC

EXTREME DeWALT® XLR FULL HEAD CARBIDE DRILL BITS BULK PACKS

COMING
IN
2009


Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT8950QZ	5	110	50	10	1	5035048078105	TBC
DT8951QZ	5	160	100	10	1	5035048078112	TBC
DT8952QZ	5	210	150	10	1	5035048078129	TBC
DT8953QZ	5.5	110	50	10	1	5035048078136	TBC
DT8954QZ	5.5	160	100	10	1	5035048078143	TBC
DT8955QZ	6	110	50	10	1	5035048078150	TBC
DT8956QZ	6	160	100	10	1	5035048078167	TBC
DT8957QZ	6	210	150	10	1	5035048078174	TBC
DT8958QZ	6	260	200	10	1	5035048078181	TBC
DT8959QZ	6.5	160	100	10	1	5035048078198	TBC
DT8960QZ	6.5	210	150	10	1	5035048078204	TBC
DT8961QZ	6.5	260	200	10	1	5035048078211	TBC
DT8962QZ	7	160	100	10	1	5035048078228	TBC
DT8963QZ	7	260	150	10	1	5035048078235	TBC
DT8964QZ	8	110	50	10	1	5035048078242	TBC
DT8965QZ	8	160	100	10	1	5035048078259	TBC
DT8966QZ	8	210	150	10	1	5035048078266	TBC
DT8967QZ	10	160	100	10	1	5035048078273	TBC
DT8968QZ	10	210	150	10	1	5035048078280	TBC
DT8969QZ	10	260	200	10	1	5035048078297	TBC
DT8970QZ	10	310	260	10	1	5035048078303	TBC
DT8971QZ	12	160	100	10	1	5035048078310	TBC
DT8972QZ	12	200	150	10	1	5035048078327	TBC

EXTREME DeWALT® FULL HEAD CARBIDE DRILL BIT SETS

COMING
IN
2009

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT8976QZ	7 piece set in metal cassette	5, 6x2, 8x2, 10, 12	7	1	5035048078341	TBC
DT8977QZ	Medium Tough Case with SDS+ XLR Full Head Carbide drill bits	5 x 110, 6 x 110 (x2), 6 x 160 (x2), 6.5 x 160, 8 x 160 (x2), 10 x 160, 12 x 160	10	1	5035048078358	TBC

SDS-PLUS 4-CUTTER DRILL BITS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT9680QZ	16	250	200	1	1	5035048066133	30.52
DT9681QZ	16	450	400	1	1	5035048066140	35.93
DT9682QZ	18	250	200	1	1	5035048066157	32.76
DT9683QZ	18	450	400	1	1	5035048066164	37.98
DT9684QZ	20	250	200	1	1	5035048066171	34.90
DT9685QZ	20	450	400	1	1	5035048066188	43.99
DT9686QZ	22	250	200	1	1	5035048066195	45.25
DT9687QZ	22	450	400	1	1	5035048066201	50.45
DT9688QZ	24	250	200	1	1	5035048066218	51.57
DT9689QZ	24	450	400	1	1	5035048066225	54.42
DT9690QZ	25	250	200	1	1	5035048066232	55.26
DT9691QZ	25	450	400	1	1	5035048066249	56.35
DT9692QZ	26	450	400	1	1	5035048066256	61.30
DT9693QZ	28	250	200	1	1	5035048066263	69.08
DT9694QZ	28	450	400	1	1	5035048066270	72.21
DT9695QZ	30	250	200	1	1	5035048066287	77.27
DT9696QZ	30	450	400	1	1	5035048066294	82.64



APPLICATIONS

- For fixing holes and through holes 16mm - 30mm.

FEATURES

- 4 flute spiral with maximum flute entry enables faster debris removal.
- Maximised central core enables more efficient energy transmission to the drill bit head.
- Fully supported carbide head gives longer life and cleaner, more concentric holes for better fixing retention.
- Open head design ensures faster drilling.



**FOR USE WITH
SDS-MAX
HAMMER DRILLS**



APPLICATIONS


- For use with SDS-Max drive hammer drills (Hilti type F,G or Y) for anchor, fixing or clearance holes in masonry concrete, brick or block work.

FEATURES

- 4 flute spiral with maximum flute entry enables faster debris removal.
- Maximised central core enables more efficient energy transmission to the drill bit head.
- Fully supported carbide head gives longer life and cleaner, more concentric holes for better fixing retention.
- Open head design ensures faster drilling.



SDS-MAX HAMMER DRILL BITS



Cat. No.	Diameter mm	Length mm	Working Length mm	Cutters	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT9400QZ	12	340	200	2	1	1	5035048059678	27.56
DT9401QZ	12	540	400	2	1	1	5035048059685	34.41
DT9402QZ	12	670	550	2	1	1	5035048059692	45.88
DT9403QZ	13	340	200	2	1	1	5035048059708	32.16
DT9404QZ	13	540	400	2	1	1	5035048059715	36.66
DT9405QZ	14	340	200	2	1	1	5035048059722	34.41
DT9406QZ	14	540	400	2	1	1	5035048059739	39.03
DT9407QZ	15	340	200	2	1	1	5035048059746	38.80
DT9408QZ	15	540	400	2	1	1	5035048059753	40.03
DT9409QZ	16	340	200	4	1	1	5035048059760	46.05
DT9410QZ	16	540	400	4	1	1	5035048059777	42.56
DT9411QZ	18	340	200	4	1	1	5035048059784	41.28
DT9412QZ	18	540	400	4	1	1	5035048059791	42.56
DT9413QZ	19	340	200	4	1	1	5035048059807	43.41
DT9414QZ	19	540	400	4	1	1	5035048059814	44.53
DT9415QZ	19	670	550	4	1	1	5035048059821	55.78
DT9416QZ	20	340	200	4	1	1	5035048059838	45.88
DT9417QZ	20	540	400	4	1	1	5035048059845	50.05
DT9418QZ	20	920	800	4	1	1	5035048059852	95.42
DT9419QZ	22	340	200	4	1	1	5035048059869	48.13
DT9420QZ	22	540	400	4	1	1	5035048059876	50.05
DT9421QZ	22	920	800	4	1	1	5035048059883	97.11
DT9422QZ	24	340	200	4	1	1	5035048059890	50.38
DT9423QZ	24	540	400	4	1	1	5035048059906	55.31
DT9424QZ	25	340	200	4	1	1	5035048059913	54.65
DT9425QZ	25	540	400	4	1	1	5035048059920	59.55
DT9426QZ	25	920	800	4	1	1	5035048059937	143.39
DT9427QZ	26	340	200	4	1	1	5035048059944	66.12
DT9428QZ	26	540	400	4	1	1	5035048059951	68.37
DT9429QZ	28	380	250	4	1	1	5035048059968	70.62
DT9430QZ	28	570	450	4	1	1	5035048059975	70.85
DT9431QZ	28	670	550	4	1	1	5035048059982	81.64
DT9432QZ	30	380	250	4	1	1	5035048059999	67.47
DT9433QZ	30	570	450	4	1	1	5035048060001	67.53
DT9434QZ	32	380	250	4	1	1	5035048060018	69.27
DT9435QZ	32	570	450	4	1	1	5035048060025	70.23
DT9436QZ	32	920	800	4	1	1	5035048060032	147.88
DT9437QZ	35	380	250	4	1	1	5035048060049	72.87
DT9438QZ	35	570	450	4	1	1	5035048060056	86.03
DT9439QZ	35	670	550	4	1	1	5035048060063	101.55
DT9440QZ	36	570	450	4	1	1	5035048060070	103.80
DT9441QZ	38	380	250	4	1	1	5035048060087	77.37
DT9442QZ	38	570	450	4	1	1	5035048060094	106.05
DT9443QZ	38	670	550	4	1	1	5035048060100	122.40
DT9444QZ	40	380	250	4	1	1	5035048060117	80.97
DT9445QZ	40	570	450	4	1	1	5035048060124	122.47
DT9446QZ	40	920	800	4	1	1	5035048060131	190.95
DT9447QZ	42	570	450	4	1	1	5035048060148	124.60
DT9448QZ	45	570	450	4	1	1	5035048060155	202.99
DT9449QZ	50	570	450	4	1	1	5035048060162	214.34
DT9450QZ	52	570	450	4	1	1	5035048060179	222.89

CHISELS

DeWALT offers you a wide range of chisels and chisel fittings to cover every application you may encounter. A variety of working lengths, widths and working end types are available to suit any machine type and user preference.

All DeWALT chisels are manufactured to the highest standards using only top quality raw materials and processes to deliver long life, durability and consistently high performance.



EXTREME DEWALT® SDS-MAX CHISELS

Cat. No.	Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6813QZ	Pointed 300mm	-	300	1	1	5035048080436	34.34
DT6814QZ	Pointed 400mm	-	400	1	1	5035048080443	42.40
DT6815QZ	Flat 25 x 300mm	25	300	1	1	5035048080450	34.34
DT6816QZ	Flat 25 x 400mm	25	400	1	1	5035048080467	42.40
DT6817QZ	Pointed 560mm	-	560	1	1	5035048080474	NOT UK

FOR USE WITH SDS-MAX COMBI HAMMERS AND BREAKERS



FEATURES

- New working end design with more material in the wear area for longer chisel life.
- Larger working end breaks more concrete in a single impact leading to greater productivity.
- Wider working end design lessens jamming issues.




**FOR USE WITH
SDS-PLUS
HAMMER DRILLS**

APPLICATIONS

- For light chipping and chiselling of tile, mortar, glazing compounds and other masonry products with hammers with a rotation stop feature.


**FOR USE WITH
SDS-MAX
HAMMER DRILLS**
FEATURES

- DeWALT has a wide range of chisels covering most common applications. Specially toughened steel and micro-processor controlled heat treatment ensures consistent tough bits with long life.


**SDS CHISELS
SDS-PLUS CHISELS**


Cat. No.	Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6801QZ	Pointed	-	250	1	1	5011402371426	15.19
DT6802QZ	Flat	20	250	1	1	5011402371433	15.19
DT6803QZ	Flat	40	200	1	1	5011402371440	19.31
DT6804QZ	Sliding Chasing	22	250	1	1	5011402371457	34.45
DT6805QZ	Hollow/Gouge	22	240	1	1	5011402371464	23.11
DT6806QZ	Tile Chisel	40	200	1	1	5011402371471	24.03
DT6807QZ	TCT Comb	32	130	1	1	5011402371488	79.90
DT6810QZ	TCT Comb	32	200	1	1	5035048014301	NOT UK



Cat. No.	Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6820QZ	Pointed	-	300	1	1	5011402378067	23.96
DT6821QZ	Pointed	-	400	1	1	5011402378104	23.96
DT8087QZ	Pointed	-	600	1	1	5035048061411	30.68
DT6822QZ	Flat	25	300	1	1	5011402378074	23.96
DT6823QZ	Flat	25	400	1	1	5011402378111	23.96
DT6824QZ	Flat	50	360	1	1	5011402378128	41.78
DT6825QZ	Flat	80	300	1	1	5011402378081	47.73
DT8088QZ	Flat	25	600	1	1	5035048061428	56.74
DT6826QZ	Hollow/Gouge	26	300	1	1	5011402378098	41.78
DT6832QZ	Sliding Chasing	32	300	1	1	5035048034217	52.07

**SDS CHISELS
SDS-MAX CHISELS**


Cat. No.	Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6833QZ	Sliding Chasing	35	380	1	1	5035048034224	88.73
DT6834QZ	Tile Chisel	80	300	1	1	5035048034231	46.78
DT6837QZ	TCT Comb Chisel	38	280	1	1	5035048034248	111.90
DT6838QZ	Bush Hammer	45	240	1	1	5035048034255	122.24
DT8090QZ	Clay Spade	110	400	1	1	5035048034514	85.16
DT8091QZ	Asphalt Cutter	90	400	1	1	5035048034521	75.47
DT8092QZ	Earth Rod Driver	13	260	1	1	5035048034538	67.34
DT8093QZ	Earth Rod Driver	16.5	260	1	1	5035048034545	71.36
DT8094QZ	Tamping Plate	150	150	1	1	5035048034552	134.66
DT8095QZ	Shank End for Tamping Plate	-	300	1	1	5035048034569	41.18

19MM HEXAGON CHISELS


Cat. No.	Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6940QZ	Pointed	-	400	1	1	5035048025031	17.60
DT6941QZ	Pointed	-	600	1	1	5035048025048	22.27
DT6942QZ	Flat	25	400	1	1	5035048025055	17.60
DT6943QZ	Flat	25	600	1	1	5035048025062	22.27
DT6944QZ	Flat	60	300	1	1	5035048025079	38.63
DT6945QZ	Flat	60	450	1	1	5035048025086	40.90
DT6946QZ	Flat wide	140	350	1	1	5035048025093	40.99
DT6939QZ	Earth Rod Driver	16	260	1	1	5035048058886	78.24
DT6947QZ	Clay Spade	115	400	1	1	5035048058893	100.67
DT6948QZ	Asphalt Cutter	90	400	1	1	5035048058909	74.13
DT6949QZ	Shank End for Tamping Plate	-	300	1	1	5035048058916	31.26

**FOR USE WITH
SDS-MAX
HAMMER DRILLS**

APPLICATIONS

- For heavy duty chiselling, channelling, and demolition tasks in concrete, stone (medium hardness), floor and wall tiles, general masonry and mortar.


**FOR USE WITH
LARGE DEMOLITION
HAMMERS
19MM HEX**
APPLICATIONS

- For heavy duty chiselling, channelling, and demolition tasks in concrete, stone (medium hardness), floor and wall tiles, general masonry and mortar.



FOR USE WITH HAMMER DRILLS



APPLICATIONS

- Heavy duty breaking of concrete, asphalt & stone. Heavy duty tamping tasks and earth rod driving.

FOR USE WITH SDS-PLUS HAMMER DRILLS



APPLICATIONS

- For fitting drainage and water pipes, heating pipes, switches, junction & distribution boxes.

FOR USE WITH SDS-MAX HAMMER DRILLS



APPLICATIONS

- For clean round holes in blocks, bricks and light concrete.

PAVEMENT BREAKER CHISELS



Cat. No.	Description	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6927QZ	Bull Point 28mm	1	1	5035048070505	31.06
DT6928QZ	Clay Spade 28mm	1	1	5035048070512	110.67
DT6929QZ	Cold Chisel 28mm	1	1	5035048070529	31.06
DT6932QZ	Scaling Tool 28mm	1	1	5035048070536	42.49
DT6933QZ	Ground Rod Driver 28mm	1	1	5035048070543	110.67
DT6934QZ	Asphalt Cutter 28mm	1	1	5035048070550	96.39
DT6935QZ	Tamper Shank 28mm	1	1	5035048070567	74.97
DT6936QZ	Tamping Plate	1	1	5035048070574	138.88

LIGHT DUTY SDS-PLUS CORE DRILLS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6740QZ	30	72	1	1	5035048013595	46.64
DT6741QZ	35	72	1	1	5035048013601	48.41
DT6742QZ	40	72	1	1	5035048013618	48.94
DT6743QZ	45	72	1	1	5035048013625	53.55
DT6744QZ	50	72	1	1	5035048013632	61.53
DT6745QZ	68	72	1	1	5035048013649	85.25
DT6746QZ	72	72	1	1	5035048013656	99.50
DT6747QZ	80	72	1	1	5035048013663	112.99
DT6748QZ	90	72	1	1	5035048013670	125.57

HEAVY DUTY SDS-MAX CORE DRILLS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6760QZ	40	107	1	1	5035048013724	90.93
DT6761QZ	50	107	1	1	5035048013731	102.33
DT6762QZ	68	107	1	1	5035048013748	113.69
DT6763QZ	80	107	1	1	5035048013755	136.39
DT6764QZ	90	107	1	1	5035048013762	159.15
DT6765QZ	100	107	1	1	5035048013779	170.50
DT6766QZ	125	107	1	1	5035048013786	204.61

ADAPTERS



LIGHT DUTY CORE ADAPTERS

Cat. No.	Description	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6750QZ	SDS-Plus adapter	110	1	1	5035048013687	15.08
DT6751QZ	SDS-Plus adapter	300	1	1	5035048013694	30.15
DT6752QZ	Hex adapter	110	1	1	5035048013700	26.61
DT6753QZ	Pilot drill	120	1	1	5035048013717	10.28

HEAVY DUTY CORE ADAPTERS



Cat. No.	Description	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6770QZ	SDS-Max Adapter	180	1	1	5035048013793	45.46
DT6771QZ	SDS-Max Adapter	400	1	1	5035048013809	70.47
DT6772QZ	Pilot bit	155	1	1	5035048013816	10.76
DT6773QZ	Extension Piece	280	1	1	5035048013823	74.22

SINGLE PIECE CORES



Cat. No.	Description	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6780QZ	SDS-Max core	50	300	1	1	5035048013830	74.22
DT6783QZ	SDS-Max core	68	300	1	1	5035048013847	87.04
DT6784QZ	SDS-Max core	80	300	1	1	5035048013854	93.28
DT6785QZ	Pilot bit	-	185	1	1	5035048013908	90.18

THROUGH DRILLING BITS



Cat. No.	Description	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6790QZ	SDS-Max through drilling bit	55	550	1	1	5035048013861	466.53
DT6791QZ	SDS-Max through drilling bit	65	550	1	1	5035048013878	548.71
DT6792QZ	SDS-Max through drilling bit	80	550	1	1	5035048013885	636.17
DT6793QZ	Pilot bit	-	88	1	1	5035048013892	31.81

DRIVE ADAPTERS



Cat. No.	Description	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6830QZ	SDS-Max to SDS-Plus	1	1	5011402378135	90.60
DT6831QZ	SDS-Max to Large Spline	1	1	5011402378671	103.23

ADAPTER - SDS-PLUS



Cat. No.	Description	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT7030QZ	SDS-Plus – 1/2" x 20 UNF (Chuck adapter)	1	1	5011402371419	90.64
DT6829QZ	SDS-Plus – 1/2" x 20 UNF chuck adapter / screwdriver bit holder	1	1	5035048034170	17.54

FOR USE WITH LIGHT AND HEAVY DUTY CORE DRILL BITS

- To be used with light duty SDS+ core drills - must be used with a pilot bit.

- For drilling through holes (55 to 80mm diameter) up to 550mm depth in concrete and masonry.

- Allows interchangeability between tool & hammer bit fitments.

- Allows use of round shank drill bits in SDS+ fitment hammers.
USE IN ROTARY MODE ONLY.

METAL DRILLING

MANUFACTURING

DeWALT drill bit factory in Buchelberg, Germany produces high performance products that respond to the needs of the professional user. Only the highest quality High Speed Steel is used to guarantee the best heat resistance and durability whilst state of the art grinding technology is used to ensure that every drill bit delivers maximum precision.

QUALITY CONTROL

DeWALT's engineers ensure every drill bit produced by its production processes complies with strict internal tolerances as well as exacting European manufacturing standards and norms (eg German Manufacturing standard DIN 338).

LEADERSHIP PRODUCT

The standard DeWALT range satisfies the application needs of the professional end user but EXTREME 2 METAL drill bits offer outstanding drilling speed as well as a hole quality that is second to none plus excellent durability. EXTREME COBALT bits are also available in order to offer users drilling into stainless steel the same performance advantages.



STATIONARY HARD MATERIALS DRILL BITS

For exceptionally long life in stationary applications in the hardest materials.



EXTREME DEWALT® COBALT DRILL BITS

For EXCEPTIONAL PERFORMANCE in Portable or Stationary drilling applications - hard materials alloyed or non alloyed steels, non ferrous metals, stainless steels up to 1100/N/mm². FASTER DRILLING - CLEANER HOLES - INCREASED DURABILITY.



EXTREME DEWALT® 2 METAL DRILL BITS

For EXCEPTIONAL PERFORMANCE in Portable or Stationary drilling applications - alloyed or non alloyed steel, non ferrous metals up to 900/N/mm², sheet metal, thin plate, wood and plastics. FASTER DRILLING - CLEANER HOLES - INCREASED DURABILITY.



HSS-G DRILL BITS

For portable or stationary drilling in vast iron, alloyed and non-alloyed steel, non-ferrous metals up to 900N/mm² wood and plastic.



STEP DRILL BITS

For drilling holes and enlarging existing holes in metal from 14mm up to 34mm.



IMPACT DRIVER DRILL BITS

Designed specifically for use with impact drivers in alloyed / non-alloyed steel, non-ferrous metals, sheet metal, thin plate wood and plastics. FASTER DRILLING, CLEANER HOLES - INCREASED DURABILITY



SUITABLE FOR THE FOLLOWING MATERIALS



Stainless Steel



Steel



Iron



Nickel



Brass




Wood



Plastic

STATIONARY HARD MATERIAL DRILL BITS SINGLE PACKS

COMING
IN
2009



Cat. No.	Diameter	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (€)
DT504000Z	1.0mm	34	12	2	1	5035048081310	TBC
DT504010Z	1.5mm	40	14	2	1	5035048081327	TBC
DT504020Z	1.6mm	43	20	2	1	5035048081334	TBC
DT504030Z	2.0mm	49	24	2	1	5035048081341	TBC
DT504040Z	2.5mm	57	30	2	1	5035048081358	TBC
DT504050Z	3.0mm	61	33	2	1	5035048081365	TBC
DT504060Z	3.1mm	65	36	2	1	5035048081375	TBC
DT504070Z	3.2mm	65	36	2	1	5035048081389	TBC
DT504080Z	3.3mm	65	36	2	1	5035048081396	TBC
DT504090Z	3.5mm	70	39	2	1	5035048081402	TBC
DT504100Z	3.7mm	70	39	2	1	5035048081419	TBC
DT504110Z	4.0mm	75	43	2	1	5035048081426	TBC
DT504120Z	4.1mm	75	43	1	1	5035048081433	TBC
DT504130Z	4.2mm	75	43	1	1	5035048081440	TBC
DT504140Z	4.5mm	80	47	1	1	5035048081457	TBC
DT504150Z	4.8mm	86	52	1	1	5035048081464	TBC
DT504160Z	4.9mm	86	52	1	1	5035048081471	TBC
DT504170Z	5.0mm	86	52	1	1	5035048081488	TBC
DT504180Z	5.1mm	86	52	1	1	5035048081495	TBC
DT504190Z	5.2mm	86	52	1	1	5035048081501	TBC
DT504200Z	5.5mm	93	57	1	1	5035048081518	TBC
DT504210Z	6.0mm	101	63	1	1	5035048081525	TBC
DT504220Z	6.1mm	101	63	1	1	5035048081532	TBC
DT504230Z	6.5mm	101	63	1	1	5035048081549	TBC
DT504240Z	6.8mm	109	69	1	1	5035048081556	TBC
DT504250Z	7.0mm	109	69	1	1	5035048081563	TBC
DT504260Z	7.5mm	109	69	1	1	5035048081570	TBC
DT504270Z	7.8mm	117	75	1	1	5035048081587	TBC
DT504280Z	7.9mm	117	75	1	1	5035048081594	TBC
DT504290Z	8.0mm	117	75	1	1	5035048081600	TBC
DT504300Z	8.5mm	117	75	1	1	5035048081617	TBC
DT504310Z	9.0mm	125	81	1	1	5035048081624	TBC
DT504320Z	9.5mm	125	81	1	1	5035048081631	TBC
DT504330Z	10.0mm	133	87	1	1	5035048081648	TBC
DT504340Z	10.2mm	133	87	1	1	5035048081655	TBC
DT504350Z	10.5mm	133	87	1	1	5035048081662	TBC
DT504360Z	11.0mm	142	94	1	1	5035048081679	TBC
DT504370Z	11.5mm	142	94	1	1	5035048081686	TBC
DT504380Z	12.0mm	151	101	1	1	5035048081693	TBC
DT504390Z	12.5mm	151	101	1	1	5035048081709	TBC
DT504400Z	13.0mm	151	101	1	1	5035048081716	TBC

FOR USE IN
DRILL PRESS OR
CNC MACHINE



APPLICATIONS

- Designed for stationary drilling of high alloy content steels and metals with a tensile strength up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels.

FEATURES


- Designed to return maximum life in hard materials (e.g. stainless steel or cast iron) when used in CNC or drill press applications.
- Each drill bit is coated to aid heat dissipation and vastly extend drill bit life.
- Full range of diameters to cover all major applications.



FOR USE WITH
CORDLESS AND
CORED DRILLS



Steel Iron Graphite



Nickel Brass Stainless Steel

APPLICATIONS

- Suitable for portable or stationary drilling of high alloy content steels and metals with a tensile strength up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels.

FEATURES

- Faster drilling - up to 4x faster than standard HSS-R drill bits.
- Increased durability - up to 50% stronger than standard HSS-R drill bits.
- Cleaner, more accurate, burr-free holes due to recessed cutting wings.
- Innovative tapered web greatly reduces breakage.
- No-Slip shank with 3 flats eliminates slipping in the chuck (diameters 5.0mm and above only).
- Gold Ferrous Oxide coating prevents overheating for longer bit life.
- 5% cobalt alloyed High Speed Steel for stability at high temperatures when drilling tough materials.

HSS-CO EXTREME DEWALT® COBALT DRILL BITS

SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5630QZ	1.0	34	12	2	1	5035048076958	NOT UK
DT5631QZ	1.5	40	18	2	1	5035048076965	NOT UK
DT5632QZ	1.6	43	20	2	1	5035048076972	NOT UK
DT5403QZ	2	49	24	2	1	5011402375912	3.65
DT5404QZ	2.5	57	30	2	1	5011402375936	3.92
DT5405QZ	3	61	33	2	1	5011402375950	4.21
DT5633QZ	3.1	65	36	2	1	5035048076988	NOT UK
DT5634QZ	3.3	65	36	2	1	5035048076996	NOT UK
DT5408QZ	3.5	70	39	2	1	5011402375974	4.98
DT5409QZ	4	75	43	2	1	5011402375998	5.44
DT5635QZ	4.1	75	43	1	1	5035048077009	NOT UK
DT5636QZ	4.2	75	43	1	1	5035048077016	NOT UK
DT5412QZ	4.5	80	47	1	1	5011402376018	3.16
DT5637QZ	4.9	86	46	1	1	5035048077023	NOT UK
DT5414QZ	5	86	52	1	1	5011402376032	3.45
DT5638QZ	5.1	86	46	1	1	5035048077030	NOT UK
DT5415QZ	5.5	93	57	1	1	5011402376056	4.12
DT5416QZ	6	93	57	1	1	5011402376070	4.12
DT5639QZ	6.1	101	58	1	1	5035048077047	NOT UK
DT5417QZ	6.5	101	63	1	1	5011402376094	4.80
DT5640QZ	6.8	109	66	1	1	5035048077054	NOT UK
DT5418QZ	7	109	69	1	1	5011402376117	5.37
DT5641QZ	7.5	109	66	1	1	5035048077061	NOT UK
DT5642QZ	7.8	117	75	1	1	5035048077078	NOT UK
DT5643QZ	7.9	117	75	1	1	5035048077085	NOT UK
DT5419QZ	8	117	75	1	1	5011402376131	5.98
DT5644QZ	8.5	117	72	1	1	5035048077092	NOT UK
DT5421QZ	9	125	81	1	1	5011402376155	7.64
DT5645QZ	9.5	125	78	1	1	5035048077108	NOT UK
DT5422QZ	10	133	87	1	1	5011402376179	8.72
DT5646QZ	10.2	133	84	1	1	5035048077115	NOT UK
DT5647QZ	10.5	133	84	1	1	5035048077122	10.51
DT5424QZ	11	142	94	1	1	5011402376193	NOT UK
DT5648QZ	11.5	142	91	1	1	5035048077139	NOT UK
DT5426QZ	12	151	101	1	1	5011402376216	13.90
DT5649QZ	12.2	151	98	1	1	5035048077146	NOT UK
DT5650QZ	12.5	151	98	1	1	5035048077153	NOT UK
DT5427QZ	13	151	101	1	1	5011402376230	16.68

HSS-CO EXTREME DEWALT® COBALT DRILL BITS

BULK PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5660QZ	1.5	40	18	10	1	5035048077160	NOT UK
DT5661QZ	1.6	43	20	10	1	5035048077177	NOT UK
DT5442QZ	2	49	24	10	1	5011402384518	15.34
DT5443QZ	2.5	57	30	10	1	5011402384525	17.19
DT5444QZ	3	61	33	10	1	5011402384532	18.92
DT5662QZ	3.1	65	36	10	1	5035048077184	NOT UK
DT5446QZ	3.2	65	36	10	1	5011402384549	19.66
DT5447QZ	3.3	65	36	10	1	5011402386208	21.77
DT5448QZ	3.5	70	39	10	1	5011402384563	22.64
DT5449QZ	4	75	43	10	1	5011402384570	24.49
DT5450QZ	4.1	75	43	10	1	5011402384587	NOT UK
DT5451QZ	4.2	75	43	10	1	5011402384594	26.35
DT5452QZ	4.5	80	47	10	1	5011402384600	28.46
DT5453QZ	4.8	86	52	10	1	5011402384617	30.43
DT5663QZ	4.9	86	46	10	1	5035048077191	NOT UK
DT5454QZ	5	86	52	10	1	5011402384624	31.05
DT5455QZ	5.1	86	52	10	1	5011402384631	NOT UK
DT5456QZ	5.2	86	52	10	1	5011402384648	37.11
DT5457QZ	5.5	93	57	10	1	5011402384655	37.11
DT5458QZ	6	93	57	10	1	5011402384662	37.11
DT5664QZ	6.1	101	58	10	1	5035048077207	NOT UK
DT5459QZ	6.5	101	63	10	1	5011402384679	43.30
DT5460QZ	6.8	109	69	10	1	5011402384686	NOT UK
DT5461QZ	7	109	69	10	1	5011402384693	48.38
DT5462QZ	7.5	109	69	10	1	5011402384709	51.95
DT5665QZ	7.8	117	75	10	1	5035048077214	NOT UK
DT5666QZ	7.9	117	75	10	1	5035048077221	NOT UK
DT5463QZ	8	117	75	10	1	5011402384716	56.29
DT5464QZ	8.5	117	75	10	1	5011402384723	66.31
DT5465QZ	9	125	81	10	1	5011402384730	68.04
DT5466QZ	9.5	125	81	10	1	5011402384747	77.32
DT5467QZ	10	133	87	10	1	5011402384754	83.51
DT5468QZ	10.2	133	87	10	1	5011402384761	91.78
DT5667QZ	10.5	133	84	5	1	5035048077238	NOT UK
DT5469QZ	11	142	94	5	1	5011402384778	51.02
DT5668QZ	11.5	142	91	5	1	5035048077245	NOT UK
DT5470QZ	12	151	101	5	1	5011402384785	62.59
DT5669QZ	12.2	151	98	5	1	5035048077252	NOT UK
DT5670QZ	12.5	151	98	5	1	5035048077269	75.02
DT5471QZ	13	151	101	5	1	5011402384792	NOT UK

HSS-CO EXTREME DEWALT® COBALT DRILL BITS SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5940QZ	6 piece set in plastic cassette	2, 3, 4, 5, 6, 8	6	1	5011402376254	26.11
DT7942QZ	Small tough case with EXTREME DEWALT® Cobalt bits	1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13 mm.	13	1	5035048066003	50.60
DT5928QZ	29 piece Cobalt set in plastic case	1, 1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13 mm.	29	1	5035048077412	192.30

FOR USE WITH CORDLESS AND CORDED DRILLS



DRILLING



**FOR USE WITH
CORDLESS AND
Corded DRILLS**



APPLICATIONS

- Suitable for portable drilling of steel, alloyed and non-alloyed up to 900 N/mm².
- For drilling sheet or thin materials (suitable for use in wood and plastics).

FEATURES


- Faster drilling - up to 4x faster than standard HSS-R drill bits.
- Increased durability - up to 50% stronger than standard HSS-R drill bits.
- Cleaner, more accurate, burr-free holes due to recessed cutting wings.
- Innovative tapered web greatly reduces breakage.
- No-Slip shank with 3 flats eliminates slipping in the chuck (diameters 5.0mm and above only).
- Gold Ferrous Oxide coating prevents overheating for longer bit life.

EXTREME DEWALT® 2 METAL DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5034QZ	1	34	12	2	1	5035048034767	2.69
DT5035QZ	1.5	40	18	2	1	5035048034774	2.83
DT5600QZ	1.6	43	20	2	1	5035048076811	NOT UK
DT5036QZ	2	49	24	2	1	5035048034781	2.96
DT5037QZ	2.5	57	30	2	1	5035048034798	3.20
DT5038QZ	3	61	33	2	1	5035048034804	3.79
DT5601QZ	3.1	65	36	2	1	5035048076828	NOT UK
DT5039QZ	3.2	65	36	2	1	5035048034811	4.18
DT5040QZ	3.3	65	36	2	1	5035048034828	4.10
DT5041QZ	3.5	70	39	2	1	5035048034835	4.42
DT5042QZ	4	75	43	2	1	5035048034842	4.70
DT5063QZ	4.1	75	43	1	1	5035048052648	2.43
DT5043QZ	4.2	75	43	1	1	5035048034859	2.47
DT0044QZ	4.5	80	46	1	1	5035048034866	2.48
DT5045QZ	4.8	86	46	1	1	5035048034873	2.60
DT5602QZ	4.9	86	46	1	1	5035048076835	NOT UK
DT5046QZ	5	86	46	1	1	5035048034880	2.69
DT5064QZ	5.1	86	46	1	1	5035048052655	2.82
DT5065QZ	5.2	86	46	1	1	5035048052662	2.90
DT5066QZ	5.4	93	52	1	1	5035048052679	2.90
DT5047QZ	5.5	93	57	1	1	5035048034897	2.92
DT5048QZ	6	93	57	1	1	5035048034903	2.92
DT5603QZ	6.1	101	58	1	1	5035048076842	NOT UK
DT5049QZ	6.5	101	58	1	1	5035048034910	3.32
DT5067QZ	6.8	109	66	1	1	5035048052686	NOT UK
DT5050QZ	7	109	66	1	1	5035048034927	3.79
DT5051QZ	7.5	109	66	1	1	5035048034934	4.28
DT5604QZ	7.8	117	75	1	1	5035048076859	NOT UK
DT5605QZ	7.9	117	75	1	1	5035048076866	NOT UK
DT5052QZ	8	117	72	1	1	5035048034941	4.40
DT5053QZ	8.5	117	72	1	1	5035048034958	5.18
DT5054QZ	9	125	78	1	1	5035048034965	5.69
DT5055QZ	9.5	125	78	1	1	5035048034972	6.30
DT5056QZ	10	133	84	1	1	5035048034989	6.95
DT5606QZ	10.2	133	84	1	1	5035048076873	NOT UK
DT5057QZ	10.5	133	84	1	1	5035048034996	7.25
DT5058QZ	11	142	91	1	1	5035048052006	8.33
DT5059QZ	11.5	142	91	1	1	5035048052013	8.81
DT5068QZ	11.8	151	98	1	1	5035048052693	9.44
DT5060QZ	12	151	98	1	1	5035048052020	10.17
DT5061QZ	12.5	151	98	1	1	5035048052037	10.27
DT5062QZ	13	151	98	1	1	5035048052044	10.52

EXTREME DEWALT® 2 METAL DRILL BITS BULK PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5535QZ	1	34	12	10	1	5035048052051	8.84
DT5536QZ	1.5	40	18	10	1	5035048052068	9.09
DT5615QZ	1.6	43	20	10	1	5035048076880	NOT UK
DT5537QZ	2	49	24	10	1	5035048052075	9.09
DT5538QZ	2.5	57	30	10	1	5035048052082	9.75
DT5539QZ	3	61	33	10	1	5035048052099	10.67
DT5616QZ	3.1	65	36	10	1	5035048076897	NOT UK
DT5540QZ	3.2	65	36	10	1	5035048052105	16.21
DT5541QZ	3.3	65	36	10	1	5035048052112	16.21
DT5542QZ	3.5	70	39	10	1	5035048052129	16.84
DT5543QZ	4	75	43	10	1	5035048052136	17.34
DT5566QZ	4.1	75	43	10	1	5035048052709	17.63
DT5544QZ	4.2	75	43	10	1	5035048052143	17.86
DT5545QZ	4.5	80	46	10	1	5035048052150	18.57
DT5546QZ	4.8	86	46	10	1	5035048052167	22.00
DT5617QZ	4.9	86	46	10	1	5035048076903	NOT UK
DT5547QZ	5	86	46	10	1	5035048052174	22.39
DT5567QZ	5.1	86	46	10	1	5035048052716	22.62
DT5568QZ	5.2	86	46	10	1	5035048052723	23.01
DT5569QZ	5.4	93	52	10	1	5035048052730	23.30
DT5548QZ	5.5	93	57	10	1	5035048052181	23.55
DT5549QZ	6	93	57	10	1	5035048052198	24.57
DT5618QZ	6.1	101	58	10	1	5035048076910	NOT UK
DT5550QZ	6.5	101	58	10	1	5035048052204	26.72
DT5570QZ	6.8	109	66	10	1	5035048052747	29.71
DT5551QZ	7	109	66	10	1	5035048052211	31.36
DT5552QZ	7.5	109	66	10	1	5035048052228	33.48
DT5619QZ	7.8	117	75	10	1	5035048076927	NOT UK
DT5620QZ	7.9	117	75	10	1	5035048076934	NOT UK
DT5553QZ	8	117	72	10	1	5035048052235	36.47
DT5554QZ	8.5	117	72	10	1	5035048052242	41.20
DT5555QZ	9	125	78	10	1	5035048052259	44.93
DT5556QZ	9.5	125	78	10	1	5035048052266	49.16
DT5557QZ	10	133	84	10	1	5035048052273	57.45
DT5621QZ	10.2	133	84	10	1	5035048076941	NOT UK
DT5558QZ	10.5	133	84	10	1	5035048052280	63.24
DT5559QZ	11	142	91	10	1	5035048052297	68.22
DT5560QZ	11.5	142	91	10	1	5035048052303	72.22
DT5571QZ	11.8	151	98	10	1	5035048052754	76.62
DT5561QZ	12	151	98	10	1	5035048052310	78.65
DT5562QZ	12.5	151	98	10	1	5035048052327	83.85
DT5563QZ	13	151	98	10	1	5035048052334	89.05

EXTREME DEWALT® 2 METAL DRILL BIT SETS

See page 55 for details.



FOR USE WITH
CORDLESS AND
Corded DRILLS



APPLICATIONS

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

FEATURES

- Precision ground twist drill bit for rapid drilling, long life and excellent concentricity.
- Ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle.
- Diameter tolerance to h8.
- Drills above 13mm (1/2") have a shank reduced to 12.7mm.

HSS-G DIN 338 JOBBER METAL DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5201QZ	1	34	12	2	1	5011402373437	2.15
DT5200QZ	1.1	36	14	2	1	5035048080481	NOT UK
DT5207QZ	1.2	38	16	2	1	5035048080498	NOT UK
DT5210QZ	1.3	38	16	2	1	5035048080504	NOT UK
DT5223QZ	1.4	40	18	2	1	5035048080511	NOT UK
DT5202QZ	1.5	40	18	2	1	5011402373451	2.27
DT5225QZ	1.6	43	20	2	1	5035048080528	NOT UK
DT5231QZ	1.7	43	20	2	1	5035048080535	NOT UK
DT5236QZ	1.8	46	22	2	1	5035048080542	NOT UK
DT5237QZ	1.9	46	22	2	1	5035048080559	NOT UK
DT5203QZ	2	49	24	2	1	5011402373475	2.27
DT5238QZ	2.1	49	24	2	1	5035048080566	NOT UK
DT5239QZ	2.2	53	27	2	1	5035048080573	NOT UK
DT5240QZ	2.3	53	27	2	1	5035048080580	NOT UK
DT5241QZ	2.4	57	30	2	1	5035048080597	NOT UK
DT5204QZ	2.5	57	30	2	1	5011402373499	2.27
DT5242QZ	2.6	57	30	2	1	5035048080603	NOT UK
DT5243QZ	2.7	61	33	2	1	5035048080610	NOT UK
DT5244QZ	2.8	61	33	2	1	5035048080627	NOT UK
DT5245QZ	2.9	61	33	2	1	5035048080634	NOT UK
DT5205QZ	3	61	33	2	1	5011402373512	2.51
DT5246QZ	3.1	65	36	2	1	5035048080641	NOT UK
DT5206QZ	3.2	65	36	2	1	5011402373536	NOT UK
DT5247QZ	3.3	65	36	2	1	5035048080656	NOT UK
DT5248QZ	3.4	70	39	2	1	5035048080665	NOT UK
DT5208QZ	3.5	70	39	2	1	5011402373574	2.98
DT5249QZ	3.6	70	39	2	1	5035048080672	NOT UK
DT5250QZ	3.7	70	39	2	1	5035048080689	NOT UK
DT5251QZ	3.8	75	43	2	1	5035048080696	NOT UK
DT5252QZ	3.9	75	43	2	1	5035048080702	NOT UK
DT5209QZ	4	75	43	2	1	5011402373598	3.11
DT5253QZ	4.1	75	43	1	1	5035048080719	NOT UK
DT5211QZ	4.2	75	43	1	1	5011402373635	1.81
DT5254QZ	4.3	80	47	1	1	5035048080726	NOT UK
DT5269QZ	4.4	80	47	1	1	5035048080747	NOT UK
DT5212QZ	4.5	80	47	1	1	5011402373659	1.83
DT5270QZ	4.6	80	47	1	1	50350480807484	NOT UK
DT5271QZ	4.7	80	47	1	1	50350480807491	NOT UK
DT5213QZ	4.8	86	52	1	1	5011402373673	1.83
DT5272QZ	4.9	86	52	1	1	50350480807507	NOT UK
DT5214QZ	5	86	52	1	1	5011402373697	1.83
DT5273QZ	5.1	86	52	1	1	503504808076514	NOT UK
DT5274QZ	5.2	86	52	1	1	503504808076521	NOT UK
DT5275QZ	5.3	86	52	1	1	503504808076538	NOT UK
DT5276QZ	5.4	93	57	1	1	503504808076545	NOT UK
DT5215QZ	5.5	93	57	1	1	5011402373710	2.33
DT5277QZ	5.6	93	57	1	1	503504808076552	NOT UK
DT5278QZ	5.7	93	57	1	1	503504808076569	NOT UK
DT5279QZ	5.8	93	57	1	1	503504808076576	NOT UK
DT5280QZ	5.9	93	57	1	1	503504808076583	NOT UK
DT5216QZ	6	101	63	1	1	5011402373734	2.51
DT5281QZ	6.1	101	63	1	1	503504808076590	NOT UK
DT5282QZ	6.2	101	63	1	1	503504808076605	NOT UK
DT5283QZ	6.3	101	63	1	1	503504808076613	NOT UK
DT5284QZ	6.4	101	63	1	1	503504808076620	NOT UK
DT5217QZ	6.5	101	63	1	1	5011402373758	2.85
DT5285QZ	6.6	101	63	1	1	503504808076637	NOT UK
DT5255QZ	6.7	101	63	1	1	5035048080773	NOT UK
DT5256QZ	6.8	109	69	1	1	50350480807740	NOT UK
DT5257QZ	6.9	109	69	1	1	50350480807757	NOT UK
DT5218QZ	7	109	69	1	1	5011402373772	NOT UK
DT5258QZ	7.1	109	69	1	1	5035048080764	NOT UK
DT5259QZ	7.2	109	69	1	1	5035048080771	NOT UK
DT5286QZ	7.3	109	69	1	1	5035048080788	NOT UK
DT5287QZ	7.4	109	69	1	1	5035048080795	NOT UK
DT5232QZ	7.5	109	69	1	1	5011402384488	4.18

HSS-G DIN 338 JOBBER METAL DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5288QZ	7.6	117	75	1	1	5035048080801	NOT UK
DT5289QZ	7.7	117	75	1	1	5035048080818	NOT UK
DT5290QZ	7.8	117	75	1	1	5035048080825	NOT UK
DT5291QZ	7.9	117	75	1	1	5035048080832	NOT UK
DT5292QZ	8	117	75	1	1	5011402373796	3.58
DT5293QZ	8.1	117	75	1	1	5035048080849	NOT UK
DT5294QZ	8.3	117	75	1	1	5035048080863	NOT UK
DT5295QZ	8.4	117	75	1	1	5035048080870	NOT UK
DT5220QZ	8.5	117	75	1	1	5011402373819	4.48
DT5296QZ	8.6	125	81	1	1	5035048080887	NOT UK
DT5297QZ	8.7	125	81	1	1	5035048080894	NOT UK
DT5298QZ	8.8	125	81	1	1	5035048080900	NOT UK
DT5299QZ	8.9	125	81	1	1	5035048080917	NOT UK
DT5221QZ	9	125	81	1	1	5011402373833	4.53
DT5400QZ	9.1	125	81	1	1	5035048080924	NOT UK
DT5401QZ	9.2	125	81	1	1	5035048080931	NOT UK
DT5402QZ	9.3	125	81	1	1	5035048080948	NOT UK
DT5406QZ	9.4	125	81	1	1	5035048080955	NOT UK
DT5407QZ	9.5	125	81	1	1	5035048080962	NOT UK
DT5410QZ	9.6	133	87	1	1	5035048080979	NOT UK
DT5411QZ	9.7	133	87	1	1	5035048080986	NOT UK
DT5413QZ	9.8	133	87	1	1	5035048080993	NOT UK
DT5420QZ	9.9	133	87	1	1	5035048081006	NOT UK
DT5222QZ	10	133	87	1	1	5011402373857	5.13
DT5423QZ	10.2	133	87	1	1	5035048081013	NOT UK
DT5425QZ	10.5	133	87	1	1	5035048081020	NOT UK
DT5224QZ	11	142	94	1	1	5011402373895	NOT UK
DT5428QZ	11.5	142	94	1	1	5035048081037	NOT UK
DT5226QZ	12	151	101	1	1	5011402373932	9.04
DT5429QZ	12.5	151	101	1	1	5035048081044	NOT UK
DT5227QZ	13	151	101	1	1	5011402373956	10.17
DT5430QZ	13.5	151	101	1	1	5035048081051	NOT UK
DT5228QZ	14	160	108	1	1	5011402373970	13.12
DT5431QZ	14.5	160	108	1	1	5035048081068	NOT UK
DT5229QZ	15	169	114	1	1	5011402373994	14.92
DT5432QZ	15.5	169	114	1	1	5035048081075	NOT UK
DT5230QZ	16	178	120	1	1	5011402374014	16.12
DT5433QZ	16.5	178	120	1	1	5035048081082	NOT UK
DT5434QZ	17	178	120	1	1	5035048081099	NOT UK
DT5435QZ	17.5	178	120	1	1	5035048081105	NOT UK
DT5436QZ	18	191	130	1	1	5035048081112	NOT UK
DT5437QZ	18.5	191	130	1	1	5035048081129	NOT UK
DT5438QZ	19	198	135	1	1	5035048081136	NOT UK
DT5439QZ	19.5	198	135	1	1	5035048081143	NOT UK
DT5472QZ	20	205	140</td				

FOR USE WITH
CORDLESS AND
Corded Drills




APPLICATIONS

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

FEATURES


- Precision ground twist drill bit for rapid drilling, long life and excellent concentricity.
- Ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle.
- Diameter tolerance to h8.
- Drills above 13mm (1/2") have a shank reduced to 12.7mm.

HSS-G DIN 338 JOBBER METAL DRILL BITS BULK PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5301QZ	1	34	12	10	1	5011402383504	11.36
DT5302QZ	1.1	36	14	10	1	5011402383511	11.36
DT5303QZ	1.2	38	16	10	1	5011402383528	11.36
DT5304QZ	1.3	38	16	10	1	5011402383535	11.36
DT5305QZ	1.4	40	18	10	1	5011402383542	11.36
DT5306QZ	1.5	40	18	10	1	5011402383559	10.01
DT5307QZ	1.6	43	20	10	1	5011402383566	10.01
DT5308QZ	1.7	43	20	10	1	5011402383573	10.01
DT5309QZ	1.8	46	22	10	1	5011402383580	10.01
DT5310QZ	1.9	46	22	10	1	5011402383597	10.01
DT5311QZ	2	49	24	10	1	5011402383603	9.00
DT5312QZ	2.1	49	24	10	1	5011402383610	9.00
DT5313QZ	2.2	53	27	10	1	5011402383627	9.00
DT5314QZ	2.3	53	27	10	1	5011402383634	9.00
DT5315QZ	2.4	57	30	10	1	5011402383641	9.00
DT5316QZ	2.5	57	30	10	1	5011402383658	9.00
DT5317QZ	2.6	57	30	10	1	5011402383665	9.00
DT5318QZ	2.7	61	33	10	1	5011402383672	9.00
DT5319QZ	2.8	61	33	10	1	5011402383689	9.34
DT5320QZ	2.9	61	33	10	1	5011402383696	9.34
DT5321QZ	3	61	33	10	1	5011402383702	9.34
DT5322QZ	3.1	65	36	10	1	5011402383719	9.34
DT5323QZ	3.2	65	36	10	1	5011402383726	9.34
DT5325QZ	3.3	65	36	10	1	5011402383740	9.34
DT5326QZ	3.4	70	39	10	1	5011402383757	9.34
DT5327QZ	3.5	70	39	10	1	5011402383764	10.01
DT5328QZ	3.6	70	39	10	1	5011402383771	10.01
DT5329QZ	3.7	70	39	10	1	5011402383788	10.01
DT5330QZ	3.8	75	43	10	1	5011402383795	11.25
DT5331QZ	3.9	75	43	10	1	5011402383801	11.25
DT5332QZ	4	75	43	10	1	5011402383818	11.25
DT5333QZ	4.1	75	43	10	1	5011402383825	11.25
DT5334QZ	4.2	75	43	10	1	5011402383832	12.49
DT5335QZ	4.3	80	47	10	1	5011402383849	12.49
DT5336QZ	4.4	80	47	10	1	5011402383856	12.49
DT5337QZ	4.5	80	47	10	1	5011402383863	12.49
DT5338QZ	4.6	80	47	10	1	5011402383870	12.49
DT5339QZ	4.7	80	47	10	1	5011402383887	13.27
DT5340QZ	4.8	86	52	10	1	5011402383894	13.27
DT5341QZ	4.9	86	52	10	1	5011402383900	13.27
DT5342QZ	5	86	52	10	1	5011402383917	14.17
DT5343QZ	5.1	86	52	10	1	5011402383924	14.17
DT5344QZ	5.2	86	52	10	1	5011402383931	14.17
DT5345QZ	5.3	86	52	10	1	5011402383948	16.54
DT5346QZ	5.4	93	57	10	1	5011402383955	16.54
DT5347QZ	5.5	93	57	10	1	5011402383962	16.54
DT5348QZ	5.6	93	57	10	1	5011402383979	18.67
DT5349QZ	5.7	93	57	10	1	5011402383986	18.67
DT5350QZ	5.8	93	57	10	1	5011402383993	18.67
DT5351QZ	5.9	93	57	10	1	5011402384006	18.67
DT5352QZ	6	93	57	10	1	5011402384013	18.67
DT5353QZ	6.1	101	63	10	1	5011402384020	21.37
DT5354QZ	6.2	101	63	10	1	5011402384037	21.37
DT5355QZ	6.3	101	63	10	1	5011402384044	21.3
DT5356QZ	6.4	101	63	10	1	5011402384051	21.37
DT5357QZ	6.5	101	63	10	1	5011402384068	21.37
DT5358QZ	6.6	101	63	10	1	5011402384075	21.37
DT5359QZ	6.7	101	63	10	1	5011402384082	24.52
DT5360QZ	6.8	109	69	10	1	5011402384099	24.52
DT5361QZ	6.9	109	69	10	1	5011402384105	24.52
DT5362QZ	7	109	69	10	1	5011402384112	24.52
DT5363QZ	7.100	109	69	10	1	5011402384129	27.80

HSS-G DIN 338 JOBBER METAL DRILL BITS BULK PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5364QZ	7.2	109	69	10	1	5011402384136	27.89
DT5365QZ	7.3	109	69	10	1	5011402384143	27.89
DT5366QZ	7.4	109	69	10	1	5011402384150	27.89
DT5367QZ	7.5	109	69	10	1	5011402384167	27.89
DT5368QZ	7.6	117	75	10	1	5011402384174	31.38
DT5369QZ	7.7	117	75	10	1	5011402384181	31.38
DT5370QZ	7.8	117	75	10	1	5011402384198	31.38
DT5371QZ	7.9	117	75	10	1	5011402384204	31.38
DT5372QZ	8	117	75	10	1	5011402384211	31.38
DT5373QZ	8.1	117	75	10	1	5011402384228	35.65
DT5374QZ	8.2	117	75	10	1	5011402384235	35.65
DT5375QZ	8.3	117	75	10	1	5011402384242	35.65
DT5376QZ	8.4	117	75	10	1	5011402384259	35.65
DT5377QZ	8.5	117	75	10	1	5011402384266	35.65
DT5378QZ	8.6	125	81	10	1	5011402384273	40.26
DT5379QZ	8.7	125	81	10	1	5011402384280	40.26
DT5380QZ	8.8	125	81	10	1	5011402384297	40.26
DT5381QZ	8.9	125	81	10	1	5011402384303	40.26
DT5382QZ	9	125	81	10	1	5011402384310	40.26
DT5383QZ	9.1	125	81	10	1	5011402384327	44.98
DT5384QZ	9.2	125	81	10	1	5011402384334	44.98
DT5385QZ	9.3	125	81	10	1	5011402384341	44.98
DT5386QZ	9.4	125	81	10	1	5011402384358	44.98
DT5387QZ	9.5	125	81	10	1	5011402384365	44.98
DT5388QZ	9.6	133	87	10	1	5011402384372	50.50
DT5389QZ	9.7	133	87	10	1	5011402384389	50.50
DT5390QZ	9.8	133	87	10	1	5011402384396	50.50
DT5391QZ	9.9	133	87	10	1	5011402384402	50.50
DT5392QZ	10	133	87	10	1	5011402384419	50.50
DT5473QZ	10.2	133	87	5	1	5035048081167	28.11
DT5393QZ	10.5	133	87	5	1	5011402384426	28.11
DT5394QZ	11	142	94	5	1	5011402384433	31.21
DT5395QZ	11.5	142	94	5	1	5011402384440	34.86
DT5396QZ	12	151	101	5	1	5011402384457	38.41
DT5397QZ	12.5	151	101	5	1	5011402384464	42.56
DT5398QZ	13	151	101	5	1	5011402384471	46.95

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5776QZ	1.56	85	55	10	1	5035048081174	NOT UK
DT5701QZ	2	85	55	10	1	5011402385317	19.30
DT5702QZ	2.5	95	66	10	1	5011402385324	20.91
DT5707QZ	3	100	66	10	1	5011402385331	20.04
DT5777QZ	3.1	100	66	10			

FOR USE WITH
CORDLESS AND
CordED DRILLS



APPLICATIONS

- Used either portable or stationary for drilling of deep holes in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

FEATURES

- For drilling and enlarging existing holes from 14mm up to 34mm

HSS-G DIN 340 LONG SERIES METAL DRILL BITS

BULK PACKS

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5722QZ	4.5	126	82	10	1	5011402385409	29.44
DT5725QZ	4.8	132	87	10	1	5011402385416	31.05
DT5779QZ	4.9	132	87	10	1	5035048081204	NOT UK
DT5726QZ	5	132	87	10	1	5011402385423	31.05
DT5727QZ	5.1	132	87	10	1	5011402385430	33.52
DT5731QZ	5.5	139	91	10	1	5011402385447	36.98
DT5736QZ	6	139	91	10	1	5011402385454	37.36
DT5780QZ	6.1	139	91	10	1	50335048081211	NOT UK
DT5741QZ	6.5	148	97	10	1	5011402385461	48.37
DT5781QZ	6.8	148	97	10	1	5035048081228	NOT UK
DT5746QZ	7	156	102	10	1	5011402385478	55.17
DT5748QZ	7.5	156	102	10	1	5011402385485	64.70
DT5782QZ	7.8	156	102	10	1	5035048081235	NOT UK
DT5783QZ	7.9	156	102	10	1	5035048081242	NOT UK
DT5749QZ	8	165	109	10	1	5011402385492	58.82
DT5784QZ	8.5	165	109	10	1	5035048081259	NOT UK
DT5751QZ	9	175	115	10	1	5011402385508	78.43
DT5785QZ	9.5	175	115	10	1	5035048081266	NOT UK
DT5753QZ	10	184	121	10	1	5011402385515	103.66
DT5786QZ	10.2	184	121	5	1	5035048081273	NOT UK
DT5787QZ	10.5	184	121	5	1	5035048081280	NOT UK
DT5759QZ	11	195	128	5	1	5011402385522	60.19
DT5788QZ	11.5	195	128	5	1	5035048081297	NOT UK
DT5757QZ	12	200	134	5	1	5011402385539	69.89
DT5789QZ	12.5	200	134	5	1	5035048081303	NOT UK
DT5759QZ	13	205	134	5	1	5011402385546	76.87

STEP DRILLS



Cat. No.

Description

Pack Qty.

M.O.Q.

Barcode

List Price Ex. VAT (£)

DT5026QZ 4-12mm Step Drill

1 1 5035048077276 TBC

DT5027QZ 6-18mm Step Drill

1 1 5035048077283 TBC

DT5030QZ 14-25mm Step Drill

1 1 5035048077290 TBC

DT5031QZ 20-34mm Step Drill

1 1 5035048077306 TBC

IMPACT DRIVER DRILL BITS

SINGLE PACKS



Cat. No.

Diameter mm

Length mm

Working Length mm

Pack Qty.

M.O.Q.

Barcode

List Price Ex. VAT (£)

DT50600QZ 3 64 26 1 1 5035048081723 TBC

DT50601QZ 3.2 67 29 1 1 5035048081730 TBC

DT50602QZ 3.5 70 29 1 1 5035048081747 TBC

DT50603QZ 4 71 30 1 1 5035048081754 TBC

DT50604QZ 4.2 71 31 1 1 5035048081761 TBC

DT50605QZ 4.5 75 31 1 1 5035048081778 TBC

DT50606QZ 4.8 76 32 1 1 5035048081785 TBC

DT50607QZ 5 78 33 1 1 5035048081792 TBC

DT50608QZ 5.5 78 35 1 1 5035048081808 TBC

DT50609QZ 6 80 37 1 1 5035048081815 TBC

DT50610QZ 6.5 81 38 1 1 5035048081822 TBC

DT50611QZ 7 89 45 1 1 5035048081839 TBC

DT50612QZ 7.5 95 50 1 1 5035048081846 TBC

DT50613QZ 8 102 50 1 1 5035048081853 TBC

DT50614QZ 8.5 102 50 1 1 5035048081860 TBC

DT50615QZ 9 102 50 1 1 5035048081877 TBC

DT50616QZ 10 102 50 1 1 5035048081884 TBC

DT50617QZ 11 102 50 1 1 5035048081891 TBC

DT50618QZ 12 102 50 1 1 5035048081897 TBC

DT50619QZ 13 102 50 1 1 5035048081914 TBC

DRILLING

WOOD DRILLING

HIGH PERFORMANCE RANGE

The DeWALT range of wood drilling bits is designed to include a wide range of hole diameters as well as drilling depths to cover the maximum of application requirements for the professional user. Whether hole quality, drilling speed or durability are required the DeWALT range has the solution.



SELECTING THE RIGHT DRILL BIT

BRAD POINT BITS

For drilling in hardboard, plywood, chipboard and natural hard and softwoods. Applications include dowelling and wood screw clearance holes.



TCT HINGE BORING BITS

For drilling flat bottom recess holes in hardboard, plywood, chipboard, and hard and softwoods. Applications include fitting cantilever hinges.



WOOD AUGER BITS

For rapid drilling of deep holes in plywood, chipboard, hard and softwoods. Applications include boring through beams, joists, doors etc.



EXTREME DeWALT® FLATWOOD BITS

For faster drilling and extended life in soft and hard woods, chipboard and other man-made materials. Applications include pipe / electrical clearance holes.




FLAT WOOD BITS

For fast, relatively clean drilling in hard and softwoods, chipboard and other man-made materials. Applications include pipe/electric clearance holes.



SELF-FEED BIT

EXTRA SHARP bits for very fast drilling of clean large diameter holes in hard/softwoods, and laminates.



FRAME BITS

For concrete framing applications.

SUITABLE FOR THE FOLLOWING MATERIALS



Wood



MDF



Hardboard



Chipboard



Laminates

FOR USE WITH
CORDLESS AND
Corded Drills



APPLICATIONS

- Suitable for drilling hardboard, plywood, chipboard and all natural hard and softwood.
- Typically used for doweling applications or wood screw clearance holes.

FEATURES

- Manufactured from chrome vanadium alloyed steel.
- Centre location point and outer cutting spurs for clean accurate holes.

APPLICATIONS

- For very rapid and accurate drilling of clean holes in hard/softwoods and laminates.

APPLICATIONS


- Typically used to fit cantilever hinges.

FEATURES

- Tungsten carbide tipped wood boring tool for clean accurate flat bottom recess holes.
- Hexagonal shank facilitates a firm chuck grip.

BRAD POINT WOOD DRILL BITS

SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4503QZ	3	70	46	1	1	5011402385553	1.24
DT4504QZ	4	80	52	1	1	5011402385560	1.36
DT4505QZ	5	90	60	1	1	5011402385577	1.49
DT4506QZ	6	100	66	1	1	5011402385584	1.60
DT4507QZ	7	110	72	1	1	5011402385591	1.71
DT4508QZ	8	120	80	1	1	5011402385607	2.15
DT4509QZ	9	130	84	1	1	5011402385614	2.28
DT4510QZ	10	133	90	1	1	5011402385621	2.62
DT4511QZ	11*	150	100	1	1	5011402385638	3.76
DT4512QZ	12*	155	102	1	1	5011402385645	3.87
DT4513QZ	13*	155	102	1	1	5011402385652	4.33
DT4514QZ	14*	160	107	1	1	5011402385669	5.30
DT4516QZ	16*	165	112	1	1	5011402385683	7.52
DT4518QZ	18*	200	130	1	1	5011402385690	9.54
DT4520QZ	20*	200	130	1	1	5011402385706	10.72

* For diameters 11mm and above the shank is reduced to 9.5 mm.

BRAD POINT WOOD DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4535QZ	5 piece set in plastic cassette	4, 5, 6, 8, 10	5	1	5011402385713	9.42

FRAME DRILL BITS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4870QZ	7	600	1	1	5035048014035	NOT UK
DT4871QZ	8	600	1	1	5035048014042	NOT UK
DT4872QZ	10	600	1	1	5035048014059	NOT UK
DT4873QZ	12	600	1	1	5035048014068	NOT UK
DT4874QZ	16	600	1	1	5035048014073	NOT UK
DT4875QZ	18	600	1	1	5035048014088	NOT UK
DT4876QZ	20	600	1	1	5035048014097	NOT UK
DT4877QZ	22	600	1	1	5035048014103	NOT UK

TCT HINGE BORING BITS


SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4541QZ	26	65	1	1	5011402386161	13.88
DT4542QZ	30	65	1	1	5011402386178	14.45
DT4543QZ	35	65	1	1	5011402386185	15.44

WOOD AUGER DRILL BITS

SINGLE PACKS




Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4600QZ	6 *	200	100	1	1	5011402385720	9.74
DT4602QZ	8 *	200	100	1	1	5011402385737	9.81
DT4604QZ	10 *	200	100	1	1	5011402385744	10.10
DT4606QZ	12	200	100	1	1	5011402385751	10.22
DT4608QZ	14	200	100	1	1	5011402385768	11.06
DT4610QZ	16	200	100	1	1	5011402385775	12.63
DT4612QZ	18	200	100	1	1	5011402385782	13.59
DT4614QZ	20	200	100	1	1	5011402385799	15.96
DT4615QZ	22	200	100	1	1	5011402385805	17.29
DT4616QZ	24	200	100	1	1	5011402385812	19.06
DT4618QZ	26	200	100	1	1	5011402385829	22.35
DT4619QZ	28	200	100	1	1	5011402385836	25.60
DT4620QZ	30	200	100	1	1	5011402385843	30.34
DT4621QZ	32	200	100	1	1	5011402385850	35.40
DT4632QZ	8 *	380	280	1	1	5011402385867	18.12
DT4634QZ	10 *	380	280	1	1	5011402385874	18.34
DT4636QZ	12	380	280	1	1	5011402385881	19.06
DT4638QZ	14	380	280	1	1	5011402385898	20.09
DT4640QZ	16	380	280	1	1	5011402385904	21.49
DT4642QZ	18	380	280	1	1	5011402385911	26.24
DT4644QZ	20	380	280	1	1	5011402385922	27.14
DT4645QZ	22	380	280	1	1	5011402385935	30.34
DT4646QZ	24	380	280	1	1	5011402385942	40.57
DT4648QZ	26	380	280	1	1	5011402385959	42.83
DT4649QZ	28	380	280	1	1	5011402385966	51.31
DT4650QZ	30	380	280	1	1	5011402385973	57.52
DT4651QZ	32	380	280	1	1	5011402385980	63.79

SELF FEED DRILL BITS



Cat. No.	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4575QZ	25	1	1	5035048072004	17.22
DT4576QZ	28	1	1	5035048072011	21.00
DT4577QZ	32	1	1	5035048072028	23.10
DT4578QZ	35	1	1	5035048072035	26.88
DT4579QZ	38	1	1	5035048072042	28.98
DT4580QZ	41	1	1	5035048072059	29.82
DT4581QZ	45	1	1	5035048072066	33.60
DT4582QZ	51	1	1	5035048072073	36.96
DT4583QZ	54	1	1	5035048072080	37.80
DT4584QZ	57	1	1	5035048072097	41.58
DT4585QZ	65	1	1	5035048072103	45.36
DT4586QZ	68	1	1	5035048072110	47.46
DT4587QZ	74	1	1	5035048072127	51.66
DT4588QZ	76	1	1	5035048072134	55.86
DT4589QZ	92	1	1	5035048072141	63.84
DT4590QZ	117	1	1	5035048072158	71.40
DT4591QZ	Self Feed Set - 5 pce (35mm, 38mm, 54mm, 65mm plus extension bar 140mm)				
DT4592QZ	Self Feed Extension piece 140mm				
		1	1	5035048072165	147.00
		1	1	5035048072172	19.32

FOR USE WITH
CORDLESS AND
Corded Drills



APPLICATIONS

- Typically used for boring clean precise holes through beams, joists, doors etc.

FEATURES

- 2 sharp cutting edges for extremely fast drilling in woods with reduced risk of binding.
- Aggressive 'Self feed' spur for rapid penetration into material.
- Non slip shank gives better bit retention in chuck.



FOR USE WITH
CORDLESS AND
CORED DRILLS



APPLICATIONS


- For the rapid drilling of holes in wood.
- Suitable for natural hard and soft wood, chipboard and other man made materials.
- Ideal for door locks, mortising, electrical and plumbing work.

FEATURES

- High quality chrome vanadium flat drill bit.
- Ground central point and cutting edges for accurate location and clean cutting.
- Ground chip breaker to reduce splintering providing relatively clean holes and improved drilling efficiency.



FLATWOOD DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4810QZ	10	150	1	1	5011402385997	4.59
DT4812QZ	12	150	1	1	5011402386000	4.66
DT4813QZ	13	150	1	1	5011402386017	4.72
DT4814QZ	14	150	1	1	5011402386024	5.19
DT4816QZ	16	150	1	1	5011402386031	5.38
DT4818QZ	18	150	1	1	5011402386048	5.68
DT4820QZ	20	150	1	1	5011402386055	5.77
DT4822QZ	22	150	1	1	5011402386062	5.83
DT4824QZ	24	150	1	1	5011402386079	6.08
DT4825QZ	25	150	1	1	5011402386086	6.50
DT4826QZ	26	150	1	1	5011402386093	6.79
DT4828QZ	28	150	1	1	5011402386109	7.34
DT4830QZ	30	150	1	1	5011402386116	7.73
DT4832QZ	32	150	1	1	5011402386123	8.01
DT4835QZ	35	150	1	1	5011402386130	8.91
DT4838QZ	38	150	1	1	5011402386147	9.24

FLATWOOD DRILL BIT EXTENSION

Cat. No.	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4849QZ	300 x 1/4"	1	1	5035048058923	7.35

EXTREME DEWALT® FLATWOOD DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4760QZ	6	152	1	1	5035048072936	4.20
DT4761QZ	8	152	1	1	5035048072943	4.20
DT4762QZ	10	152	1	1	5035048072950	4.86
DT4763QZ	12	152	1	1	5035048072967	4.86
DT4764QZ	13	152	1	1	5035048072974	4.86
DT4765QZ	14	152	1	1	5035048072981	4.86
DT4766QZ	16	152	1	1	5035048072998	4.92
DT4767QZ	18	152	1	1	5035048073001	5.15
DT4768QZ	20	152	1	1	5035048073018	5.36
DT4769QZ	22	152	1	1	5035048073025	5.57
DT4770QZ	24	152	1	1	5035048073032	5.79
DT4771QZ	25	152	1	1	5035048073049	6.00
DT4772QZ	26	152	1	1	5035048073056	6.22
DT4773QZ	28	152	1	1	5035048073063	6.43
DT4774QZ	30	152	1	1	5035048073070	6.64
DT4775QZ	32	152	1	1	5035048073087	6.86
DT4776QZ	35	152	1	1	5035048073094	7.60
DT4777QZ	38	152	1	1	5035048073100	7.90
DT4778QZ	40	152	1	1	5035048073117	7.93
DT7943BQZ	8 piece set (12, 16, 18, 20, 22, 25, 28, 32)	152	1	1	5035048073292	42.84

FOR USE WITH
CORDLESS AND
CORED DRILLS



APPLICATIONS

- For the rapid drilling of holes in wood.
- Suitable for natural hard and soft wood, chipboard and other man made materials.
- Ideal for door locks, mortising, electrical and plumbing work.

FEATURES

- Extra thick robust steel shank for outstanding durability and bit life.
- Chamfered outer cutting spurs for clean, very fast drilling and extended drilling life.
- Precision ground central point with optimised design for faster material penetration and increased drilling speed.



EXTREME DEWALT® 406MM FLATWOOD DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4780QZ	10	406	1	1	5035048073124	NOT UK
DT4781QZ	12	406	1	1	5035048073131	NOT UK
DT4782QZ	13	406	1	1	5035048073148	NOT UK
DT4783QZ	14	406	1	1	5035048073155	NOT UK
DT4784QZ	16	406	1	1	5035048073162	NOT UK
DT4785QZ	20	406	1	1	5035048073179	NOT UK
DT4786QZ	22	406	1	1	5035048073186	NOT UK
DT4787QZ	24	406	1	1	5035048073193	NOT UK
DT4788QZ	25	406	1	1	5035048073209	NOT UK
DT4789QZ	26	406	1	1	5035048073216	NOT UK
DT4790QZ	28	406	1	1	5035048073223	NOT UK
DT4791QZ	30	406	1	1	5035048073230	NOT UK
DT4792QZ	32	406	1	1	5035048073247	NOT UK
DT4793QZ	35	406	1	1	5035048073254	NOT UK
DT4794QZ	38	406	1	1	5035048073261	NOT UK