
PCIe-6361, PXIe-6361, and USB-6361 Specifications

Contents

PCle-6361, PXle-6361, and USB-6361 Specifications 3

PCIe-6361, PXIe-6361, and USB-6361 Specifications

PCIe-6361, PXIe-6361, and USB-6361 Specifications

The following specifications are typical at 25 °C, unless otherwise noted. For more information about the PCIe-6361, PXIe-6361, and USB-6361, refer to the ***X Series User Manual*** available from ni.com/manuals.

Device Pinouts

Figure 1. NI PCIe/PXIe-6361 Pinout




Figure 2. NI USB-6361 Mass Termination Pinout




Figure 3. NI USB-6361 Screw Terminal Pinout





Figure 4. NI USB-6361 BNC Front Panel and Pinout



Analog Input

Number of channels	8 differential or 16 single ended
ADC resolution	16 bits
DNL	No missing codes guaranteed
INL	Refer to the AI Absolute Accuracy section.

Sample rate		
Single channel maximum		2.00 MS/s
Multichannel maximum (aggregate)		1.00 MS/s
Minimum		No minimum
Timing resolution		10 ns
Timing accuracy		50 ppm of sample rate
Input coupling		DC
Input range		± 0.1 V, ± 0.2 V, ± 0.5 V, ± 1 V, ± 2 V, ± 5 V, ± 10 V
Maximum working voltage for analog inputs (signal + common mode)		± 11 V of AI GND
CMRR (DC to 60 Hz)		100 dB
Input impedance		
Device on		
AI+ to AI GND	>10 G Ω in parallel with 100 pF	
AI- to AI GND	>10 G Ω in parallel with 100 pF	

Device off	
AI+ to AI GND	820 Ω
AI- to AI GND	820 Ω
Input bias current	± 100 pA
Crosstalk (at 100 kHz)	
Adjacent channels	-75 dB
Non-adjacent channels	-95 dB
Small signal bandwidth (-3 dB)	1.7 MHz
Input FIFO size	2,047 samples
Scan list memory	4,095 entries
Data transfers	
PCIe/PXIe	DMA (scatter-gather), programmed I/O
USB	USB Signal Stream, programmed I/O
Overvoltage protection for all analog input and sense channels	
Device on	± 25 V for up to two AI pins

Device off	±15 V for up to two AI pins
Input current during overvoltage condition	±20 mA max/AI pin

Settling Time for Multichannel Measurements

Range	±60 ppm of Step (±4 LSB for Full-Scale Step)	±15 ppm of Step (±1 LSB for Full-Scale Step)
± 10 V, ±5 V, ±2 V, ±1 V	1 μs	1.5 μs
±0.5 V	1.5 μs	2 μs
±0.2 V, ±0.1 V	2 μs	8 μs

Typical Performance Graphs

Figure 5. Settling Error versus Time for Different Source Impedances




Figure 6. AI <0..15> Small Signal Bandwidth





Figure 7. AI <0..15> CMRR



AI Absolute Accuracy

Table 2. AI Absolute Accuracy

Nominal Range Positive Full Scale	Nominal Range Negative Full Scale	Residual Gain Error (ppm of Reading)	Residual Offset Error (ppm of Range)	Offset Tempco (ppm of Range/°C)	Random Noise, σ (μV_{rms})	Absolute Accuracy at Full Scale (μV)
10	-10	48	13	21	315	1,660
5	-5	55	13	21	157	870
2	-2	55	13	24	64	350
1	-1	65	17	27	38	190
0.5	-0.5	68	17	34	27	100

Nominal Range Positive Full Scale	Nominal Range Negative Full Scale	Residual Gain Error (ppm of Reading)	Residual Offset Error (ppm of Range)	Offset Tempco (ppm of Range/°C)	Random Noise, σ (μVrms)	Absolute Accuracy at Full Scale (μV)
0.2	-0.2	95	27	55	21	53
0.1	-0.1	108	45	90	17	33

For more information about absolute accuracy at full scale, refer to the [AI Absolute Accuracy Example](#) section.

Gain tempco	13 ppm/°C
Reference tempco	1 ppm/°C
INL error	60 ppm of range



Note Accuracies listed are valid for up to two years from the device external calibration.

AI Absolute Accuracy Equation

$$\text{AbsoluteAccuracy} = \text{Reading} \cdot (\text{GainError}) + \text{Range} \cdot (\text{OffsetError}) + \text{NoiseUncertainty}$$

- $\text{GainError} = \text{ResidualGainError} + \text{GainTempco} \cdot (\text{TempChangeFromLastInternalCal}) + \text{ReferenceTempco} \cdot (\text{TempChangeFromLastExternalCal})$
- $\text{OffsetError} = \text{ResidualOffsetError} + \text{OffsetTempco} \cdot (\text{TempChangeFromLastInternalCal}) + \text{INLError}$
- $\text{NoiseUncertainty} = \frac{\text{Random Noise} \cdot 3}{\sqrt{10,000}}$
for a coverage factor of 3σ and averaging 10,000 points.

AI Absolute Accuracy Example

For example, on the 10 V range, the absolute accuracy at full scale is as follows:

- GainError: $48 \text{ ppm} + 13 \text{ ppm} \cdot 1 + 1 \text{ ppm} \cdot 10 = 71 \text{ ppm}$
- OffsetError: $13 \text{ ppm} + 21 \text{ ppm} \cdot 1 + 60 \text{ ppm} = 94 \text{ ppm}$
- NoiseUncertainty:

$$\frac{315 \mu\text{V} \cdot 3}{\sqrt{10,000}}$$

$$= 9.4 \mu\text{V}$$
- AbsoluteAccuracy: $10 \text{ V} \cdot (\text{GainError}) + 10 \text{ V} \cdot (\text{OffsetError}) + \text{NoiseUncertainty} = 1,660 \mu\text{V}$

Analog Triggers

Number of triggers	1
Source	AI <0..15>, APFI 0
Functions	Start Trigger, Reference Trigger, Pause Trigger, Sample Clock, Convert Clock, Sample Clock Timebase
Source level	
AI <0..15>	±Full scale
APFI 0	±10 V
Resolution	16 bits
Modes	Analog edge triggering, analog edge triggering with hysteresis, and analog window triggering

Bandwidth (-3 dB)	
AI <0..15>	3.4 MHz
APFI 0	3.9 MHz
Accuracy	±1% of range
APFI 0 characteristics	
Input impedance	10 kΩ
Coupling	DC
Protection, power on	±30 V
Protection, power off	±15 V

Analog Output

Number of channels	2
DAC resolution	16 bits
DNL	±1 LSB
Monotonicity	16 bit guaranteed

Maximum update rate (simultaneous)	
1 channel	2.86 MS/s
2 channels	2.00 MS/s
Timing accuracy	50 ppm of sample rate
Timing resolution	10 ns
Output range	± 10 V, ± 5 V, $\pm$ external reference on APFI 0
Output coupling	DC
Output impedance	0.2Ω
Output current drive	± 5 mA
Overdrive protection	± 25 V
Overdrive current	26 mA
Power-on state	± 5 mV
Power-on/off glitch	
PCIe/PXIe	1.5 V peak for 200 ms

USB	1.5 V for 1.2 s, typical behavior ¹
Output FIFO size	8,191 samples shared among channels used
Data transfers	
PCIe/PXIe	DMA (scatter-gather), programmed I/O
USB	USB Signal Stream, programmed I/O
AO waveform modes	Non-periodic waveform, periodic waveform regeneration mode from onboard FIFO, periodic waveform regeneration from host buffer including dynamic update
Settling time, full-scale step 15 ppm (1 LSB)	2 μ s
Slew rate	20 V/ μ s
Glitch energy at midscale transition, ± 10 V range	10 nV $\cdot$ s


External Reference

APFI 0 characteristics

1. Time period may be longer due to host system USB performance. Time period is longer during firmware updates.

Input impedance	10 k Ω
Coupling	DC
Protection, device on	± 30 V
Protection, device off	± 15 V
Range	± 11 V
Slew rate	20 V/ μ s

Figure 8. AO External Reference Bandwidth



AO Absolute Accuracy (Warranted)

Table 3. AO Absolute Accuracy

Nominal Range Positive Full Scale (V)	Nominal Range Negative Full Scale (V)	Residual Gain Error (ppm of Reading)	Gain Tempco (ppm/°C)	Reference Tempco (ppm/°C)	Residual Offset Error (ppm of Range)	Offset Tempco (ppm of Range/°C)	INL Error (ppm of Range)	Absolute Accuracy at Full Scale (μV)
10	-10	63	17	1	33	2	64	1,890
5	-5	70	8	1	33	2	64	935



Note *Absolute Accuracy at Full Scale* numbers are valid immediately following self calibration and assumes the device is operating within 10 °C of the last external calibration.



Note Accuracies listed are valid for up to two years from the device external calibration.

AO Absolute Accuracy Equation

$$\text{AbsoluteAccuracy} = \text{OutputValue} \cdot (\text{GainError}) + \text{Range} \cdot (\text{OffsetError})$$

- $\text{GainError} = \text{ResidualGainError} + \text{GainTempco} \cdot (\text{TempChangeFromLastInternalCal}) + \text{ReferenceTempco} \cdot (\text{TempChangeFromLastExternalCal})$
- $\text{OffsetError} = \text{ResidualOffsetError} + \text{OffsetTempco} \cdot (\text{TempChangeFromLastInternalCal}) + \text{INLError}$

Digital I/O/PFI

Static Characteristics

Number of channels	24 total, 8 (P0.<0..7>), 16 (PFI <0..7>/P1, PFI <8..15>/P2)
Ground reference	D GND

Direction control	Each terminal individually programmable as input or output
Pull-down resistor	50 k Ω typical, 20 k Ω minimum
Input voltage protection	± 20 V on up to two pins



Caution Stresses beyond those listed under the ***Input voltage protection*** specification may cause permanent damage to the device.

Waveform Characteristics (Port 0 Only)

Terminals used	Port 0 (P0.<0..7>)
Port/sample size	Up to 8 bits
Waveform generation (DO) FIFO	2,047 samples
Waveform acquisition (DI) FIFO	255 samples
DI Sample Clock frequency	
PCIe/PXIe	0 to 10 MHz, system and bus activity dependent
USB	0 to 1 MHz, system and bus activity dependent
DO Sample Clock frequency	
PCIe/PXIe	

Regenerate from FIFO	0 to 10 MHz
Streaming from Memory	0 to 10 MHz, system and bus activity dependent
USB	
Regenerate from FIFO	0 to 10 MHz
Streaming from memory	0 to 1 MHz, system and bus activity dependent
Data transfers	
PCIe/PXIe	DMA (scatter-gather), programmed I/O
USB	USB Signal Stream, programmed I/O
Digital line filter settings	160 ns, 10.24 μ s, 5.12 ms, disable

PFI/Port 1/Port 2 Functionality

Functionality	Static digital input, static digital output, timing input, timing output
Timing output sources	Many AI, AO, counter, DI, DO timing signals
Debounce filter settings	90 ns, 5.12 μ s, 2.56 ms, custom interval, disable; programmable high and low transitions; selectable per input

Recommended Operating Conditions

Input high voltage (V_{IH})	
Minimum	2.2 V
Maximum	5.25 V
Input low voltage (V_{IL})	
Minimum	0 V
Maximum	0.8 V
Output high current (I_{OH})	
P0.<0..7>	-24 mA maximum
PFI <0..15>/P1/P2	-16 mA maximum
Output low current (I_{OL})	
P0.<0..7>	24 mA maximum
PFI <0..15>/P1/P2	16 mA maximum

Digital I/O Characteristics

Positive-going threshold (V_{T+})	2.2 V maximum
---------------------------------------	---------------

Negative-going threshold (VT-)	0.8 V minimum
Delta VT hysteresis (VT+ - VT-)	0.2 V minimum
I _{IL} input low current (V _{IN} = 0 V)	-10 µA maximum
I _{IH} input high current (V _{IN} = 5 V)	250 µA maximum

Figure 9. P0.<0..7>: I_{OH} versus V_{OH}




Figure 10. P0.<0..7>: I_{OL} versus V_{OL}




Figure 11. PFI <0..15>/P1/P2: I_{OH} versus V_{OH}





Figure 12. PFI <0..15>/P1/P2: I_{OL} versus V_{OL}



General-Purpose Counters

Number of counter/ timers	4
Resolution	32 bits
Counter measurements	Edge counting, pulse, pulse width, semi-period, period, two-edge separation

Position measurements		X1, X2, X4 quadrature encoding with Channel Z reloading; two-pulse encoding
Output applications		Pulse, pulse train with dynamic updates, frequency division, equivalent time sampling
Internal base clocks		100 MHz, 20 MHz, 100 kHz
External base clock frequency		
PCIe/USB	0 MHz to 25 MHz	
PXIe	0 MHz to 25 MHz; 0 MHz to 100 MHz on PXIe_DSTAR <A,B>	
Base clock accuracy		50 ppm
Inputs		Gate, Source, HW_Arm, Aux, A, B, Z, Up_Down, Sample Clock
Routing options for inputs		
PCIe	Any PFI, RTSI, analog trigger, many internal signals	
PXIe	Any PFI, PXIe_DSTAR<A,B>, PXI_TRIG, PXI_STAR, analog trigger, many internal signals	
USB	Any PFI, analog trigger, many internal signals	
FIFO		127 samples per counter
Data transfers		

PCIe/PXIe	Dedicated scatter-gather DMA controller for each counter/timer, programmed I/O
USB	USB Signal Stream, programmed I/O

Frequency Generator

Number of channels	1
Base clocks	20 MHz, 10 MHz, 100 kHz
Divisors	1 to 16
Base clock accuracy	50 ppm

Phase-Locked Loop (PLL)

Number of PLLs	1
----------------	---

Table 4. Reference Clock Locking Frequencies

Reference Signal	PCIe Locking Input Frequency (MHz)	PXIe Locking Input Frequency (MHz)	USB Locking Input Frequency (MHz)
PXIe_DSTAR<A,B>	—	10, 20, 100	—
PXI_STAR	—	10, 20	—
PXIe_CLK100	—	100	—
PXI_TRIG <0..7>	—	10, 20	—
RTSI <0..7>	10, 20	—	—

Reference Signal	PCIe Locking Input Frequency (MHz)	PXIe Locking Input Frequency (MHz)	USB Locking Input Frequency (MHz)
PFI <0..15>	10, 20	10, 20	10

Output of PLL	100 MHz Timebase; other signals derived from 100 MHz Timebase including 20 MHz and 100 kHz Timebases
---------------	--

External Digital Triggers

Source	
PCIe	Any PFI, RTSI
PXIe	Any PFI, PXIe_DSTAR<A,B>, PXI_TRIG, PXI_STAR
USB	Any PFI
Polarity	Software-selectable for most signals
Analog input function	Start Trigger, Reference Trigger, Pause Trigger, Sample Clock, Convert Clock, Sample Clock Timebase
Analog output function	Start Trigger, Pause Trigger, Sample Clock, Sample Clock Timebase
Counter/timer functions	Gate, Source, HW_Arm, Aux, A, B, Z, Up_Down, Sample Clock
Digital waveform generation (DO) function	Start Trigger, Pause Trigger, Sample Clock, Sample Clock Timebase

Digital waveform acquisition (DI) function	Start Trigger, Reference Trigger, Pause Trigger, Sample Clock, Sample Clock Timebase
--	--

Device-to-Device Trigger Bus

Input Source	
PCIe	RTSI <0..7> ² [2]
PXIe	PXI_TRIG <0..7>, PXI_STAR, PXIe_DSTAR<A,B>
USB	None
Output destination	
PCIe	RTSI <0..7> ² [2]
PXIe	PXI_TRIG <0..7>, PXIe_DSTARC
USB	None
Output selections	10 MHz Clock; frequency generator output; many internal signals
Debounce filter settings	90 ns, 5.12 μ s, 2.56 ms, custom interval, disable; programmable high and low transitions; selectable per input

2. In other sections of this document, RTSI refers to RTSI <0..7> for NI PCIe-6361 or PXI_TRIG <0..7> for NI PXIe-6361.

Bus Interface

PCIe	
Form factor	x1 PCI Express, specification v1.1 compliant
Slot compatibility	x1, x4, x8, and x16 PCI Express slots ³
DMA channels	8, can be used for analog input, analog output, digital input, digital output, counter/timer 0, counter/timer 1, counter/timer 2, counter/timer 3
PXIe	
Form factor	x1 PXI Express peripheral module, specification rev 1.0 compliant
Slot compatibility	x1 and x4 PXI Express or PXI Express hybrid slots
DMA channels	8, can be used for analog input, analog output, digital input, digital output, counter/timer 0, counter/timer 1, counter/timer 2, counter/timer 3

All PXIe devices may be installed in PXI Express slots or PXI Express hybrid slots.

USB	
USB compatibility	USB 2.0 Hi-Speed or full-speed ⁴

- Some motherboards reserve the x16 slot for graphics use. For PCI Express guidelines, refer to ni.com/pciexpress.
- Operating on a full-speed bus results in lower performance, and you might not be able to achieve maximum sampling/update rates.

USB Signal Stream	8, can be used for analog input, analog output, digital input, digital output, counter/timer 0, counter/timer 1, counter/timer 2, counter/timer 3
-------------------	---

Power Requirements



Caution The protection provided by the device can be impaired if the device is used in a manner not described in the ***X Series User Manual***.

PCIe	
Without disk drive power connector installed	
+3.3 V	4.6 W
+12 V	5.4 W
With disk drive power connector installed	
+3.3 V	1.6 W
+12 V	5.4 W
+5 V	15 W
PXIe	
+3.3 V	1.6 W
+12 V	19.8 W



Caution The USB device must be powered with an NI offered AC adapter or a National Electric Code (NEC) Class 2 DC source that meets the power requirements for the device and has appropriate safety certification marks for country of use.

USB	
Power supply requirements	11 to 30 VDC, 30 W, 2 positions 3.5 mm pitch pluggable screw terminal with screw locks similar to Phoenix Contact MC 1,5/2-STF-3,5 BK
Power input mating connector	Phoenix Contact MC 1,5/2-GF-3,5 BK or equivalent

Current Limits



Caution Exceeding the current limits may cause unpredictable device behavior.

PCIe	
Without disk drive power connector installed	
P0/PFI/P1/P2 and +5 V terminals combined	0.59 A max
With disk drive power connector installed	
+5 V terminal (connector 0)	1 A max ^[5] ₅
+5 V terminal (connector 1)	1 A max ^[5]
P0/PFI/P1/P2 combined	1 A max

PXIe	
+5 V terminal (connector 0)	1 A max ^[5]
+5 V terminal (connector 1)	1 A max ^[5]
P0/PFI/P1/P2 and +5 V terminals combined	2 A max
USB	
+5 V terminal	1 A max ^[5]
P0/PFI/P1/P2 and +5 V terminals combined	2 A max

Physical Characteristics

Printed circuit board dimensions	
PCIe	9.9 × 16.8 cm (3.9 × 6.6 in.) (half-length)
PXIe	Standard 3U PXI
Enclosure dimensions (includes connectors)	
USB	
Mass termination	18.5 × 17.3 × 3.6 cm (7.3 × 6.8 × 1.4 in.)
Screw terminal	26.4 × 17.3 × 3.6 cm (10.4 × 6.8 × 1.4 in.)

- Has self-resetting fuse that opens when current exceeds this specification.

BNC	20.3 × 18.5 × 6.8 cm (8.0 × 7.3 × 2.7 in.)
Weight	
PCIe	161 g (5.6 oz)
PXIe	205 g (7.2 oz)
USB Mass Termination	965 g (2 lb2.1 oz)
USB Screw Terminal	1.413 kg (3 lb1.8 oz)
USB BNC	1.52 kg (3 lb5 oz)
I/O connector	
PCIe/PXIe	1 68-pin VHDCI
USB Mass Termination	1 68-pin VHDCI
USB Screw Terminal	64 screw terminals
USB BNC	20 BNCs and 30 screw terminals

Table 5. PCIe/PXIe Mating Connectors

Manufacturer, Part Number	Description
MOLEX 71430-0011	68-Pos Right Angle Single Stack PCB-Mount VHDCI (Receptacle)

Manufacturer, Part Number	Description
MOLEX 74337-0016	68-Pos Right Angle Dual Stack PCB-Mount VHDCI (Receptacle)
MOLEX 71425-3001	68-Pos Offset IDC Cable Connector (Plug) (SHC68-*)

PCle disk drive power connector	Standard ATX peripheral connector (not serial ATA)
USB screw terminal wiring/BNC screw terminal wiring	16-24 AWG

Calibration

Recommended warm-up time	15 minutes
Calibration interval	2 years

Maximum Working Voltage

Maximum working voltage refers to the signal voltage plus the common-mode voltage.

Channel to earth	11 V, Measurement Category I
------------------	------------------------------



Caution Do not use for measurements within Categories II, III, or IV.

Shock and Vibration

Operational shock	30 g peak, half-sine, 11 ms pulse (Tested in accordance with IEC 60068-2-27. Test profile developed in accordance with MIL-PRF-28800F.)
Random vibration	
Operating	5 to 500 Hz, 0.3 grms
Nonoperating	5 to 500 Hz, 2.4 grms (Tested in accordance with IEC 60068-2-64. Nonoperating test profile exceeds the requirements of MIL-PRF-28800F, Class 3.)

Environmental

Operating temperature	
PCIe	0 to 50 °C
PXIe	0 to 55 °C
USB	0 to 45 °C
Storage temperature	-40 to 70 °C
Operating humidity	10 to 90% RH, noncondensing

Storage humidity	5 to 95% RH, noncondensing
Pollution Degree	2
Maximum altitude	2,000 m

Indoor use only.

Safety Compliance Standards

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA C22.2 No. 61010-1



Note For safety certifications, refer to the product label or the [Product Certifications and Declarations](#) section.

EMC Standards

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- ICES-001: Class A emissions



Note Group 1 equipment is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



Note In Europe, Australia, New Zealand, and Canada (per CISPR 11) Class A equipment is intended for use in non-residential locations.

CE Compliance

This product meets the essential requirements of applicable European Directives, as follows:

- 2014/35/EU; Low-Voltage Directive (safety)
- 2014/30/EU; Electromagnetic Compatibility Directive (EMC)
- 2011/65/EU; Restriction of Hazardous Substances (RoHS)
- 2014/53/EU; Radio Equipment Directive (RED)
- 2014/34/EU; Potentially Explosive Atmospheres (ATEX)

Product Certifications and Declarations

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit ni.com/product-certifications, search by model number, and click the appropriate link.

Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the ***Engineering a Healthy Planet*** web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

EU and UK Customers

-  **Waste Electrical and Electronic Equipment (WEEE)**—At the end of the product life cycle, all NI products must be disposed of according to local laws and

regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

电子信息产品污染控制管理办法（中国RoHS）

-  **中国RoHS**— NI符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于NI中国RoHS合规性信息，请登录 ni.com/environment/rohs_china。 (For information about China RoHS compliance, go to ni.com/environment/rohs_china.)