




COMPRESSION SPRINGS

Century Spring warehouses the largest inventory of high-grade, straight, cylindrically-shaped compression springs in the world. All the springs found in this section of the catalog are fabricated from round wire. Rectangular wire is sometimes employed to reduce the

solid (totally compressed) height or increase the space efficiency of the design. **Century Spring's** die springs are made from rectangular wire for this reason. (See the "Die Spring" section of this catalog.)

Selecting a Compression Spring:



Turn to the inventory page with the desired outside diameter (O.D.). Outside diameters increase as page numbers increase and are found in the left column of the page.

- Next, find the length or rate (strength) you require. These, too, are normally in increasing order.

Spring rate is the load (pounds) it takes to deflect (compress) the spring one theoretical inch, i.e., if the rate = 40 lbs./in., it would take 10 pounds to deflect it 1/4 inch, or 80 pounds for 2 inches, etc..

- If the length or rate is not known but the installed working length (W.L.) is, then select a spring — say 30% longer — than the W.L..

You must know the load at the W.L.. Just subtract the W.L. from the spring's selected free length and

multiply by its rate to obtain the load to compare with your required value.

- If the load required is not obtained, select a new candidate with either an increase or decrease in rate (strength) or free length.
- Be certain that the tabulated solid length (completely compressed) for your candidate spring indicates enough room for deflection and, also, that the deflection is not significantly greater than the tabulated "Maximum Suggested" for stress reasons.

Note: If the spring needed for your application cannot be found in our catalog inventory, we can fabricate it for you. Often, there is no cost increase for this service as we have low quantity requirements.

Design Information

The basic compression rate and wire stress for a compression spring can be estimated with the following:

$$R = \frac{Gd^4}{8nD^3} \quad \text{and} \quad R = \frac{P}{\Delta}$$

$$S = \frac{8PK}{\pi d^3} \quad \text{or} \quad S = \frac{8RDK\Delta}{\pi d^3}$$

Note: One should not employ the curvature (k) correction stress in an expression solving for deflection. Use the uncorrected stress only or errors will occur. The uncorrected stress can be used for static applications.

Large wire and bar stock sizes also require an empirically-derived reduction in the standard rate calculation of up to 9%.

For these reasons, refinements in large spring design should be left to the experienced spring designer.

Where: **D** = Mean diameter, (O.D. - d) inches

d = Wire diameter, inches

G = Modulus (spring steel = 11.5×10^6 , stainless = 10×10^6), p.s.i.

K = Stress correction factor (see plot)

N = Number of total coils

n = Number of active coils (see table)

P = Applied load, pounds

p = Pitch, distance between centerlines of wires of adjoining coils

R = Spring rate, pounds per inch (lbs./in.)

S = Wire stress, psi

Δ = Deflection, inches

$\pi = 3.14$




Design Information (continued)

The suggested maximum allowable spring-wire stress values can be derived from the "Minimum Tensile Strength" (MTS) tables found in the "Material Properties" section of this catalog. The MTS values vary with the spring-wire diameter. Further, 30 to 45 percent of the MTS value, depending on the material type, is used as a corrected stress target to produce a long fatigue life. The table, "Properties of Common Spring Materials", found also in the "Material Properties" section of this catalog, indicates the appropriate percentage value of the MTS to use for a given spring material.

For free custom spring designs, call or fax our **Custom Spring Department**. For quick stress checks on stock or custom spring designs, or technical information, call or fax our **Engineering Department**.

SPRING CHARACTERISTICS	TYPE OF ENDS			
	OPEN	OPEN & GROUND	CLOSED	CLOSED & GROUND
SOLID LENGTH	$d(N+1)$	$d \times N$	$d(N+1)$	$d \times N$
ACTIVE COILS (n)	N	$N - 1$	$N - 2$	$N - 2$
TOTAL COILS (N)	n	N	$n + 2$	$n + 2$
FREE LENGTH (L)	$(p \times N) + d$	$p \times N$	$(p \times n) + 3d$	$(p \times n) + 2d$

WAHL CURVATURE STRESS CORRECTION



Spring Characteristics

Service Life

It should be noted that if critical force-versus-deflection linearity is required, only the center 60 to 80 percent of the available deflection range should be employed. Thus, reserve at least the first and last 15 to 20 percent of the range for potential spring-end and adjacent coil-contact effects. These effects can be largely ignored for the majority of spring applications.

The column "Suggested Maximum Deflection" found in the following pages of inventory reflects the recommended inches of travel to obtain a statistical service-life of approximately 100,000 cycles (deflections) with infrequent breakage. This can be realized if the spring in question is not subjected to shock loads, rapid cycling, temperature extremes, corrosion or stress values above those previously recommended. If the spring is statically loaded (not cycling), a near-infinite life can be expected. Extended spring service-life can be expected by applying recommendations found in the "Material Properties" section of this catalog.

Materials

The highest grades of spring wire are used for fabricating our springs. To create cost-effective warehousing of our stock spring inventory for our customers, we offer material certification for custom springs only. Certifications of conformance for geometric tolerances set by the Spring Manufacturers Institute (SMI) are available for our stock springs upon request. See the "Custom Spring" section of this catalog if material trace certifications or unique materials are required.

"Spring Steel" is a stock inventory term covering:

- Music wire
- Hard-drawn (MB) wire
- Oil-tempered wire

Additionally, stock compression-spring materials include:

- Stainless Steel (300 series)
- Beryllium Copper
- Phosphor Bronze



Spring Characteristics (continued)

Tolerances

Century Spring manufactures stock springs to commercial tolerances defined by the SMI. Calculated rates and loads based on the SMI geometric tolerances have an approximate +/- ten percent. Low or high-index springs will have higher values. Compression springs characteristically have an hourglass shape when coiled on an automatic coiler; therefore, outside/inside tolerancing is applied to end coils only. This is an important consideration when selecting a spring that fits over a rod or inside a cylinder. Call us if tighter tolerance values are required.

Regarding angle tolerance, the plane of the ground end of a spring is usually within three degrees of the perpendicular-to-the-body axis of the spring.

Direction of Helix (wind)

The wind direction of our stock springs varies, both RHW and LHW. Stock springs are not sorted for wind direction. To order springs wound to a specific direction, please see page 376 for more information or contact our Custom Division at 800-237-5225.

Ends

The compression spring ends configuration is indicated in the "Ends" column of our inventory listings which are:

Closed (C) - The last coil at each end is bent back to touch the previous coil to create a flat base.

Closed and Ground (C&G) - The closed ends of a spring ground to a more accurate flat base. This will also reduce the solid length.



Open (O) - The spring end coils remain open, maintaining the spring machine's helical wind shape.

Finish

The finishes available for our compression springs are as indicated in the "Finish" column of our inventory listing which include:

Zinc
Gold Iridite
Black Oxide
Passivated (upon request)
None (can be plated upon request)

Data Required For Compression Springs



CURRENT DESIGN

Outside Diameter _____ in.

Free Length _____ in.

Wire Dia. _____ dec.

Material _____

Total Coils _____ (or pitch) _____ in.

Finish _____

SPRING TO BE DESIGNED

To work in _____ in. hole

To work over _____ in. dia. shaft

To support ____ lbs. $\pm$ ____ lbs. at _____ in.

Rate per in. _____ lbs. $\pm$

Max. solid height _____ in.

Max. deflection _____

ADD'L. INFO IF AVAILABLE

Material _____


Wind: Optional ____ Right ____ Left ____

Finish _____


Style of ends: Cl. & Grd. _____

Closed only _____

Open or Plain _____



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.036	.91	10075	.59	15.1	.022	.6	2.6	.46	.15	3.8	.39	1.7	.35	8.9	0.007	0.2	49.0	SST	C	N
0.036	.91	JJ-7	.63	15.9	.024	.6	1.6	.28	.16	4.1	.25	1.1	.25	6.2	0.006	0.2	40.0	SST	C	N
0.040	1.02	2924	.66	16.8	.020	.5	11	2.0	.13	3.2	1.4	6.4	.50	12.6	0.010	0.3	48.5	MW	C	N
0.040	1.02	10778	.69	17.5	.028	.7	1.0	.17	.35	8.9	.35	1.6	.30	7.7	0.006	0.2	49.5	MW	C	N
0.054	1.37	RR-6	.25	6.4	.036	.9	6.2	1.1	.09	2.2	.56	2.5	.16	4.1	0.009	0.2	16.5	SST	C	N
0.054	1.37	10619	.72	18.3	.038	1.0	1.6	.29	.37	9.3	.60	2.7	.32	8.1	0.008	0.2	39.0	MW	C	N
0.057	1.45	70000	.13	3.3	.045	1.1	3.7	.66	.07	1.7	.25	1.1	.04	1.0	0.006	0.2	5.75	MW	C	N
0.057	1.45	70000S	.13	3.3	.045	1.1	3.3	.57	.05	1.3	.17	.74	.04	1.0	0.006	0.2	5.75	SST	C	N
0.057	1.45	70009	.13	3.3	.043	1.1	6.9	1.2	.06	1.5	.40	1.8	.05	1.2	0.007	0.2	6.00	MW	C	N
0.057	1.45	70009S	.13	3.3	.043	1.1	6.0	1.1	.04	1.1	.26	1.2	.05	1.2	0.007	0.2	6.00	SST	C	N
0.057	1.45	70018	.13	3.3	.041	1.0	12	2.1	.05	1.2	.57	2.5	.06	1.4	0.008	0.2	6.13	MW	C	N
0.057	1.45	70018S	.13	3.3	.041	1.0	11	1.8	.03	.88	.37	1.6	.06	1.4	0.008	0.2	6.13	SST	C	N
0.057	1.45	70001	.19	4.8	.045	1.1	2.3	.40	.11	2.8	.25	1.1	.06	1.4	0.006	0.2	8.13	MW	C	N
0.057	1.45	70001S	.19	4.8	.045	1.1	2.0	.35	.08	2.1	.17	.74	.06	1.4	0.006	0.2	8.13	SST	C	N
0.057	1.45	70010	.19	4.8	.043	1.1	4.0	.70	.10	2.5	.40	1.8	.07	1.8	0.007	0.2	8.88	MW	C	N
0.057	1.45	70010S	.19	4.8	.043	1.1	3.5	.61	.07	1.9	.26	1.2	.07	1.8	0.007	0.2	8.88	SST	C	N
0.057	1.45	70019	.19	4.8	.041	1.0	7.4	1.3	.08	2.0	.57	2.5	.08	2.0	0.008	0.2	8.75	MW	C	N
0.057	1.45	70019S	.19	4.8	.041	1.0	6.4	1.1	.06	1.4	.37	1.6	.08	2.0	0.008	0.2	8.75	SST	C	N
0.057	1.45	70002	.25	6.4	.045	1.1	1.7	.30	.15	3.8	.25	1.1	.07	1.7	0.006	0.2	10.3	MW	C	N
0.057	1.45	70002S	.25	6.4	.045	1.1	1.5	.26	.11	2.8	.17	.74	.07	1.7	0.006	0.2	10.3	SST	C	N
0.057	1.45	70011	.25	6.4	.043	1.1	3.1	.54	.13	3.3	.40	1.8	.08	2.1	0.007	0.2	11.0	MW	C	N
0.057	1.45	70011S	.25	6.4	.043	1.1	2.7	.47	.10	2.5	.26	1.2	.08	2.1	0.007	0.2	11.0	SST	C	N
0.057	1.45	70020	.25	6.4	.041	1.0	5.3	.92	.11	2.8	.57	2.5	.10	2.5	0.008	0.2	11.5	MW	C	N
0.057	1.45	70020S	.25	6.4	.041	1.0	4.6	.80	.08	2.0	.37	1.6	.10	2.5	0.008	0.2	11.5	SST	C	N
0.057	1.45	70003	.31	7.9	.045	1.1	1.4	.24	.19	4.7	.25	1.1	.08	2.0	0.006	0.2	12.4	MW	C	N
0.057	1.45	70003S	.31	7.9	.045	1.1	1.2	.21	.14	3.6	.17	.74	.08	2.0	0.006	0.2	12.4	SST	C	N
0.057	1.45	70012	.31	7.9	.043	1.1	2.4	.42	.17	4.2	.40	1.8	.10	2.6	0.007	0.2	13.5	MW	C	N
0.057	1.45	70012S	.31	7.9	.043	1.1	2.1	.37	.12	3.2	.26	1.2	.10	2.6	0.007	0.2	13.5	SST	C	N
0.057	1.45	70021	.31	7.9	.041	1.0	4.1	.72	.14	3.6	.57	2.5	.12	3.1	0.008	0.2	14.3	MW	C	N
0.057	1.45	70021S	.31	7.9	.041	1.0	3.6	.62	.10	2.6	.37	1.6	.12	3.1	0.008	0.2	14.3	SST	C	N
0.057	1.45	70004	.38	9.7	.045	1.1	1.1	.19	.23	5.8	.25	1.1	.10	2.4	0.006	0.2	14.8	MW	C	N
0.057	1.45	70004S	.38	9.7	.045	1.1	.96	.17	.17	4.4	.17	.74	.10	2.4	0.006	0.2	14.8	SST	C	N
0.057	1.45	70013	.38	9.7	.043	1.1	2.0	.35	.20	5.0	.40	1.8	.12	3.0	0.007	0.2	15.8	MW	C	N
0.057	1.45	70013S	.38	9.7	.043	1.1	1.7	.31	.15	3.8	.26	1.2	.12	3.0	0.007	0.2	15.8	SST	C	N
0.057	1.45	70022	.38	9.7	.041	1.0	3.4	.59	.17	4.3	.57	2.5	.14	3.6	0.008	0.2	16.8	MW	C	N
0.057	1.45	70022S	.38	9.7	.041	1.0	3.0	.52	.12	3.1	.37	1.6	.14	3.6	0.008	0.2	16.8	SST	C	N
0.057	1.45	70005	.44	11.2	.045	1.1	.95	.17	.26	6.7	.25	1.1	.11	2.7	0.006	0.2	16.8	MW	C	N
0.057	1.45	70005S	.44	11.2	.045	1.1	.83	.14	.20	5.1	.17	.74	.11	2.7	0.006	0.2	16.8	SST	C	N
0.057	1.45	70014	.44	11.2	.043	1.1	1.7	.30	.23	5.9	.40	1.8	.14	3.4	0.007	0.2	18.3	MW	C	N
0.057	1.45	70014S	.44	11.2	.043	1.1	1.5	.26	.18	4.5	.26	1.2	.14	3.4	0.007	0.2	18.3	SST	C	N
0.057	1.45	70023	.44	11.2	.041	1.0	2.8	.50	.20	5.1	.57	2.5	.17	4.2	0.008	0.2	19.6	MW	C	N
0.057	1.45	70023S	.44	11.2	.041	1.0	2.5	.43	.15	3.8	.37	1.6	.17	4.2	0.008	0.2	19.6	SST	C	N
0.057	1.45	70006	.50	12.7	.045	1.1	.85	.15	.30	7.5	.25	1.1	.12	3.0	0.006	0.2	18.5	MW	C	N
0.057	1.45	70006S	.50	12.7	.045	1.1	.74	.13	.22	5.7	.17	.74	.12	3.0	0.006	0.2	18.5	SST	C	N
0.057	1.45	70015	.50	12.7	.043	1.1	1.5	.26	.26	6.7	.40	1.8	.15	3.8	0.007	0.2	20.4	MW	C	N
0.057	1.45	70015S	.50	12.7	.043	1.1	1.3	.23	.20	5.1	.26	1.2	.15	3.8	0.007	0.2	20.4	SST	C	N
0.057	1.45	70024	.50	12.7	.041	1.0	2.5	.43	.23	5.9	.57	2.5	.19	4.7	0.008	0.2	22.4	MW	C	N
0.057	1.45	70024S	.50	12.7	.041	1.0	2.1	.37	.17	4.3	.37	1.6	.19	4.7	0.008	0.2	22.4	SST	C	N
0.057	1.45	70007	.56	14.2	.045	1.1	.75	.13	.34	8.6	.25	1.1	.13	3.3	0.006	0.2	20.8	MW	C	N
0.057	1.45	70007S	.56	14.2	.045	1.1	.65	.11	.25	6.5	.17	.74	.13	3.3	0.006	0.2	20.8	SST	C	N
0.057	1.45	70016	.56	14.2	.043	1.1	1.3	.23	.31	7.7	.40	1.8	.17	4.3	0.007	0.2	23.3	MW	C	N
0.057	1.45	70016S	.56	14.2	.043	1.1	1.1	.20	.23	5.9	.26	1.2	.17	4.3	0.007	0.2	23.3	SST	C	N
0.057	1.45	70025	.56	14.2	.041	1.0	2.2	.39	.26	6.6	.57	2.5	.21	5.2	0.008	0.2	24.8	MW	C	N
0.057	1.45	70025S	.56	14.2	.041	1.0	1.9	.34	.19	4.8	.37	1.6	.21	5.2	0.008	0.2	24.8	SST	C	N
0.057	1.45	70008	.63	16.0	.045	1.1	.65	.11	.39	9.9	.25	1.1	.15	3.8	0.006	0.2	23.6	MW	C	N
0.057	1.45	70008S	.63	16.0	.045	1.1	.57	.10	.29	7.5	.17	.74	.15	3.8	0.006	0.2	23.6	SST	C	N
0.057	1.45	70017	.63	16.0	.043	1.1	1.2	.20	.34	8.8	.40	1.8	.19	4.8	0.007	0.2	26.0	MW	C	N
0.057	1.45	70017S	.63	16.0	.043	1.1	1.0	.18	.26	6.6	.26	1.2	.19	4.8	0.007	0.2	26.0	SST	C	N
0.057	1.45	70026	.63	16.0	.041	1.0	2.0	.35	.29	7.3	.57	2.5	.22	5						




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.062	1.57	2534	.91	23.0	.044	1.1	1.3	.23	.45	11	.60	2.7	.46	11.6	0.009	0.2	49.8	MW	C	N
0.062	1.57	N-18	.97	24.6	.052	1.3	.06	.01	.61	16	.04	.17	.36	9.0	0.005	0.1	70.0	SST	C	N
0.068	1.73	10938	.31	8.0	.046	1.2	8.1	1.4	.10	2.5	.78	3.5	.17	4.3	0.011	0.3	14.5	SST	C	N
0.068	1.73	A10-13	.34	8.7	.052	1.3	2.6	.45	.19	4.8	.49	2.2	.11	2.7	0.008	0.2	12.5	MW	C	GI
0.072	1.83	A10-3	.50	12.7	.042	1.1	56	9.8	.05	1.2	2.6	11	.15	3.8	0.015	0.4	9.00	MW	C	N
0.075	1.91	KK-29	.20	5.2	.059	1.5	4.4	.76	.10	2.6	.44	2.0	.06	1.5	0.008	0.2	6.50	MW	C	N
0.078	1.98	N-2	.19	4.8	.068	1.7	.21	.04	.12	3.0	.02	.11	.07	1.8	0.005	0.1	13.0	MW	C	N
0.078	1.98	N-11	.22	5.6	.058	1.5	9.5	1.7	.06	1.4	.53	2.3	.07	1.8	0.010	0.3	6.25	SST	C	N
0.078	1.98	N-78	.25	6.4	.068	1.7	.38	.07	.21	5.2	.08	.35	.05	1.1	0.005	0.1	8.00	MW	C	N
0.078	1.98	S-1013	.25	6.4	.050	1.3	24	4.3	.06	1.4	1.4	6.2	.15	3.7	0.014	0.4	9.50	SST	C	N
0.078	1.98	12526	.25	6.4	.048	1.2	49	8.5	.05	1.3	2.4	11	.14	3.4	0.015	0.4	8.00	MW	C	N
0.078	1.98	M-6	.25	6.4	.044	1.1	56	9.8	.04	.95	2.1	9.3	.21	5.4	0.017	0.4	11.5	MW	C	N
0.078	1.98	S-904	.28	7.1	.054	1.4	12	2.1	.07	1.9	.89	4.0	.13	3.2	0.012	0.3	9.50	SST	C	N
0.078	1.98	LL-1	.31	7.9	.046	1.2	61	11	.05	1.2	2.9	13	.15	3.9	0.016	0.4	8.50	MW	C	N
0.078	1.98	11146	.34	8.7	.054	1.4	12	2.0	.12	3.1	1.4	6.2	.14	3.7	0.012	0.3	11.0	MW	C	N
0.078	1.98	DD-73	.34	8.7	.058	1.5	5.1	.89	.16	4.1	.82	3.7	.12	3.0	0.010	0.3	11.0	MW	C	N
0.078	1.98	4345	.50	12.7	.066	1.7	.19	.03	.32	8.2	.06	.27	.18	4.5	0.006	0.2	28.5	MW	C	N
0.078	1.98	10213	1.13	28.6	.054	1.4	2.6	.45	.54	14	1.4	6.2	.52	13.1	0.012	0.3	42.0	MW	C	Z
0.078	1.98	B4-1	1.50	38.1	.054	1.4	2.9	.51	.31	7.8	.89	4.0	.41	10.4	0.012	0.3	33.0	SST	C	N
0.083	2.11	LL-66	.25	6.4	.055	1.4	22	3.9	.06	1.5	1.3	5.9	.13	3.4	0.014	0.4	8.50	SST	C	N
0.083	2.11	NN-81	.88	22.2	.059	1.5	2.2	.38	.39	9.9	.84	3.8	.44	11.3	0.012	0.3	36.0	SST	C	N
0.084	2.13	B6-19	.28	7.0	.074	1.9	.36	.06	.00	.00	.00	.00	.04	1.0	0.005	0.1	7.00	SPR	C	N
0.088	2.24	70027	.13	3.3	.072	1.8	5.8	1.0	.07	1.7	.38	1.7	.04	1.0	0.008	0.2	4.00	MW	C	N
0.088	2.24	70027S	.13	3.3	.072	1.8	5.0	.88	.05	1.2	.24	1.1	.04	1.0	0.008	0.2	4.00	SST	C	N
0.088	2.24	70036	.13	3.3	.068	1.7	13	2.2	.06	1.5	.74	3.3	.05	1.4	0.010	0.3	4.38	MW	C	N
0.088	2.24	70036S	.13	3.3	.068	1.7	11	1.9	.04	1.1	.47	2.1	.05	1.4	0.010	0.3	4.38	SST	C	N
0.088	2.24	70047	.13	3.3	.064	1.6	26	4.5	.05	1.2	1.3	5.6	.07	1.7	0.012	0.3	4.63	MW	C	N
0.088	2.24	70047S	.13	3.3	.064	1.6	22	3.9	.04	.90	.80	3.6	.07	1.7	0.012	0.3	4.63	SST	C	N
0.088	2.24	KK-17	.19	4.7	.068	1.7	10	1.8	.07	1.9	.74	3.3	.06	1.5	0.010	0.3	5.00	MW	C	N
0.088	2.24	70028	.19	4.8	.072	1.8	3.5	.62	.11	2.7	.38	1.7	.05	1.3	0.008	0.2	5.25	MW	C	N
0.088	2.24	70028S	.19	4.8	.072	1.8	3.1	.54	.08	2.0	.24	1.1	.05	1.3	0.008	0.2	5.25	SST	C	N
0.088	2.24	70037	.19	4.8	.068	1.7	6.9	1.2	.11	2.7	.74	3.3	.07	1.9	0.010	0.3	6.38	MW	C	N
0.088	2.24	70037S	.19	4.8	.068	1.7	6.0	1.1	.08	2.0	.47	2.1	.07	1.9	0.010	0.3	6.38	SST	C	N
0.088	2.24	70048	.19	4.8	.064	1.6	15	2.6	.09	2.2	1.3	5.6	.09	2.3	0.012	0.3	6.63	MW	C	N
0.088	2.24	70048S	.19	4.8	.064	1.6	13	2.2	.06	1.6	.80	3.6	.09	2.3	0.012	0.3	6.63	SST	C	N
0.088	2.24	70029	.25	6.4	.072	1.8	2.5	.44	.15	3.9	.38	1.7	.06	1.5	0.008	0.2	6.63	MW	C	N
0.088	2.24	70029S	.25	6.4	.072	1.8	2.2	.38	.11	2.9	.24	1.1	.06	1.5	0.008	0.2	6.63	SST	C	N
0.088	2.24	70038	.25	6.4	.068	1.7	5.0	.88	.15	3.7	.74	3.3	.09	2.3	0.010	0.3	8.00	MW	C	N
0.088	2.24	70038S	.25	6.4	.068	1.7	4.4	.77	.11	2.7	.47	2.1	.09	2.3	0.010	0.3	8.00	SST	C	N
0.088	2.24	70049	.25	6.4	.064	1.6	11	1.9	.12	3.0	1.3	5.6	.11	2.9	0.012	0.3	8.38	MW	C	N
0.088	2.24	70049S	.25	6.4	.064	1.6	9.3	1.6	.09	2.2	.80	3.6	.11	2.9	0.012	0.3	8.38	SST	C	N
0.088	2.24	70030	.31	7.9	.072	1.8	2.0	.36	.19	4.8	.38	1.7	.07	1.8	0.008	0.2	7.63	MW	C	N
0.088	2.24	70030S	.31	7.9	.072	1.8	1.8	.31	.14	3.5	.24	1.1	.07	1.8	0.008	0.2	7.63	SST	C	N
0.088	2.24	70039	.31	7.9	.068	1.7	3.9	.68	.19	4.8	.74	3.3	.11	2.7	0.010	0.3	9.75	MW	C	N
0.088	2.24	70039S	.31	7.9	.068	1.7	3.4	.60	.14	3.5	.47	2.1	.11	2.7	0.010	0.3	9.75	SST	C	N
0.088	2.24	70050	.31	7.9	.064	1.6	8.2	1.4	.15	3.9	1.3	5.6	.14	3.4	0.012	0.3	10.3	MW	C	N
0.088	2.24	70050S	.31	7.9	.064	1.6	7.2	1.3	.11	2.8	.80	3.6	.14	3.4	0.012	0.3	10.3	SST	C	N
0.088	2.24	12767	.34	8.7	.056	1.4	39	6.8	.07	1.7	2.6	12	.15	3.9	0.016	0.4	8.50	MW	C	N
0.088	2.24	70031	.38	9.7	.072	1.8	1.6	.27	.25	6.2	.38	1.7	.08	2.1	0.008	0.2	9.38	MW	C	N
0.088	2.24	70031S	.38	9.7	.072	1.8	1.4	.24	.18	4.6	.24	1.1	.08	2.1	0.008	0.2	9.38	SST	C	N
0.088	2.24	70040	.38	9.7	.068	1.7	3.3	.58	.22	5.6	.74	3.3	.12	3.1	0.010	0.3	11.1	MW	C	N
0.088	2.24	70040S	.38	9.7	.068	1.7	2.9	.51	.16	4.1	.47	2.1	.12	3.1	0.010	0.3	11.1	SST	C	N
0.088	2.24	70051	.38	9.7	.064	1.6	6.6	1.2	.19	4.8	1.3	5.6	.16	4.0	0.012	0.3	12.3	MW	C	N
0.088	2.24	70051S	.38	9.7	.064	1.6	5.8	1.0	.14	3.5	.80	3.6	.16	4.0	0.012	0.3	12.3	SST	C	N
0.088	2.24	70032	.44	11.2	.072	1.8	1.4	.24	.27	7.0	.38	1.7	.09	2.3	0.008	0.2	10.3	MW	C	N
0.088	2.24	70032S	.44	11.2	.072	1.8	1.2	.21	.20	5.1	.24	1.1	.09	2.3	0.008	0.2	10.3	SST	C	N
0.088	2.24	70041	.44	11.2	.068	1.7	2.9	.50	.26	6.6	.74	3.3	.14	3.5	0.010	0.3	12.6	MW	C	N
0.088	2.24	70041S	.44	11.2	.068	1.7	2.5	.43	.19	4.8	.47	2.1	.14	3.5	0.010	0.3	12.6	SST	C	N
0.088	2.24	70052	.44	11.2	.064	1.6	5.8	1.0	.22	5.5	1.3	5.6	.18	4.5	0.012	0.3	13.8	MW	C	N
0.088	2.24	70052S	.44	11.2	<															



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.088	2.24	70056	.69	17.5	.064	1.6	3.5	.61	.36	9.1	1.3	5.6	.27	6.8	0.012	0.3	21.4	MW	C	N
0.088	2.24	70056S	.69	17.5	.064	1.6	3.0	.53	.26	6.7	.80	3.6	.27	6.8	0.012	0.3	21.4	SST	C	N
0.088	2.24	70046	.75	19.1	.068	1.7	1.6	.28	.46	12	.74	3.3	.22	5.6	0.010	0.3	20.9	MW	C	N
0.088	2.24	70046S	.75	19.1	.068	1.7	1.4	.24	.34	8.5	.47	2.1	.22	5.6	0.010	0.3	20.9	SST	C	N
0.088	2.24	70057	.75	19.1	.064	1.6	3.1	.54	.40	10	1.3	5.6	.30	7.6	0.012	0.3	23.9	MW	C	N
0.088	2.24	70057S	.75	19.1	.064	1.6	2.7	.47	.30	7.5	.80	3.6	.30	7.6	0.012	0.3	23.9	SST	C	N
0.092	2.34	11161	.50	12.7	.072	1.8	1.6	.29	.33	8.5	.55	2.4	.12	3.0	0.010	0.3	11.0	BC	C	N
0.094	2.39	EE-21	.13	3.2	.066	1.7	48	8.4	.02	.63	1.2	5.2	.07	1.8	0.014	0.4	4.00	SST	C	N
0.094	2.39	S-1010	.14	3.6	.054	1.4	144	25	.01	.25	1.4	6.4	.13	3.3	0.020	0.5	5.50	SST	C	N
0.094	2.39	3719	.16	4.0	.068	1.7	24	4.2	.06	1.6	1.5	6.6	.08	2.1	0.013	0.3	5.25	MW	C	N
0.094	2.39	BB-5	.17	4.3	.078	2.0	2.3	.41	.12	2.9	.27	1.2	.06	1.4	0.008	0.2	6.00	MW	C	N
0.094	2.39	O-23	.19	4.7	.074	1.9	2.7	.47	.07	1.7	.18	.80	.12	3.0	0.010	0.3	11.0	MW	C	Z
0.094	2.39	2870	.19	4.8	.072	1.8	7.2	1.3	.10	2.5	.71	3.1	.09	2.3	0.011	0.3	7.13	MW	C	Z
0.094	2.39	II-22	.22	5.5	.074	1.9	1.9	.33	.06	1.5	.11	.48	.16	4.1	0.010	0.3	15.0	MW	C	N
0.094	2.39	BB-21	.22	5.6	.078	2.0	2.7	.47	.09	2.2	.23	1.0	.05	1.2	0.008	0.2	5.00	SST	C	N
0.094	2.39	N-79	.25	6.4	.084	2.1	.18	.03	.20	5.1	.04	.16	.05	1.3	0.005	0.1	9.00	MW	C	N
0.094	2.39	JJ-68	.25	6.4	.074	1.9	4.3	.75	.10	2.6	.44	2.0	.08	2.0	0.010	0.3	7.00	SST	C	N
0.094	2.39	N-99	.25	6.4	.070	1.8	6.7	1.2	.12	3.0	.78	3.4	.13	3.4	0.012	0.3	10.1	MW	C	GI
0.094	2.39	11923	.25	6.4	.070	1.8	7.7	1.4	.13	3.3	1.0	4.5	.12	3.0	0.012	0.3	9.00	MW	C	N
0.094	2.39	3648	.25	6.4	.066	1.7	22	3.8	.09	2.2	1.9	8.2	.11	2.8	0.014	0.4	7.00	MW	C	Z
0.094	2.39	M-118	.25	6.4	.064	1.6	30	5.2	.07	1.8	2.1	9.1	.12	3.0	0.015	0.4	7.00	MW	C	Z
0.094	2.39	II-96	.25	6.4	.052	1.3	125	22	.03	.72	3.5	16	.17	4.3	0.021	0.5	7.00	SST	C	N
0.094	2.39	O-148	.28	7.1	.048	1.2	250	44	.03	.69	6.8	30	.17	4.4	0.023	0.6	6.50	MW	C	N
0.094	2.39	DD-7	.30	7.5	.068	1.7	7.7	1.4	.13	3.4	1.0	4.6	.14	3.6	0.013	0.3	10.0	HD	O	Z
0.094	2.39	LL-37	.31	7.9	.074	1.9	3.0	.53	.15	3.7	.44	2.0	.10	2.5	0.010	0.3	9.00	SST	C	N
0.094	2.39	10219	.31	7.9	.072	1.8	4.6	.81	.19	4.9	.88	3.9	.12	3.1	0.011	0.3	10.0	MW	C	N
0.094	2.39	10083	.31	7.9	.068	1.7	15	2.7	.10	2.5	1.5	6.6	.10	2.6	0.013	0.3	7.00	MW	C	N
0.094	2.39	O-56	.31	8.0	.070	1.8	5.4	.95	.16	4.0	.85	3.8	.16	4.0	0.012	0.3	12.0	MW	C	Z
0.094	2.39	00-10	.31	7.9	.052	1.3	82	14	.06	1.6	5.3	24	.20	5.2	0.021	0.5	8.75	MW	O	N
0.094	2.39	10874	.34	8.7	.064	1.6	16	2.8	.09	2.2	1.4	6.1	.17	4.3	0.015	0.4	10.3	SST	C	N
0.094	2.39	S-1526	.34	8.7	.060	1.5	35	6.2	.06	1.4	2.0	8.7	.16	4.1	0.017	0.4	8.50	SST	C	N
0.094	2.39	11113	.34	8.7	.058	1.5	43	7.5	.08	2.0	3.5	15	.20	5.0	0.018	0.5	10.0	MW	C	N
0.094	2.39	M-56	.34	8.7	.052	1.3	62	11	.06	1.4	3.5	16	.27	6.9	0.021	0.5	12.0	SST	C	N
0.094	2.39	N-315	.34	8.7	.066	1.7	13	2.4	.14	3.5	1.9	8.2	.15	3.9	0.014	0.4	10.0	MW	C	N
0.094	2.39	10932	.34	8.7	.062	1.6	24	4.2	.10	2.6	2.5	11	.18	4.6	0.016	0.4	10.3	MW	C	GI
0.094	2.39	FF-33	.38	9.5	.070	1.8	5.7	1.0	.21	5.3	1.2	5.3	.15	3.8	0.012	0.3	11.5	MW	C	N
0.094	2.39	LL-2	.38	9.5	.070	1.8	2.0	.34	.16	4.0	.31	1.4	.22	5.5	0.012	0.3	17.0	MW	C	N
0.094	2.39	3778	.38	9.5	.066	1.7	13	2.4	.14	3.5	1.9	8.2	.15	3.9	0.014	0.4	10.0	MW	C	Z
0.094	2.39	N-15	.41	10.3	.074	1.9	2.9	.50	.24	6.2	.69	3.1	.12	2.9	0.010	0.3	10.5	MW	C	N
0.094	2.39	V-92	.41	10.3	.058	1.5	43	7.5	.08	2.0	3.5	15	.20	5.0	0.018	0.5	10.0	MW	C	N
0.094	2.39	11127	.44	11.1	.066	1.7	9.0	1.6	.21	5.2	1.9	8.2	.21	5.3	0.014	0.4	14.0	MW	C	N
0.094	2.39	O-8	.44	11.1	.064	1.6	15	2.6	.14	3.5	2.1	9.1	.20	5.0	0.015	0.4	12.0	MW	C	N
0.094	2.39	2541	.44	11.1	.062	1.6	18	3.2	.14	3.5	2.5	11	.22	5.7	0.016	0.4	13.0	MW	C	Z
0.094	2.39	N-40	.44	11.1	.062	1.6	17	2.9	.15	3.8	2.5	11	.24	6.1	0.016	0.4	14.0	MW	C	Z
0.094	2.39	N-26	.44	11.1	.060	1.5	24	4.2	.12	3.1	2.9	13	.24	6.0	0.017	0.4	13.0	MW	C	N
0.094	2.39	N-149	.44	11.1	.058	1.5	31	5.4	.11	2.9	3.5	15	.26	6.5	0.018	0.5	13.3	MW	C	Z
0.094	2.39	3902	.44	11.1	.054	1.4	52	9.0	.09	2.3	4.6	21	.28	7.1	0.020	0.5	13.0	MW	C	N
0.094	2.39	CC-92	.44	11.1	.050	1.3	69	12	.09	2.2	5.9	26	.35	8.9	0.022	0.6	15.0	MW	C	Z
0.094	2.39	N-7	.47	11.9	.066	1.7	8.0	1.4	.23	5.9	1.9	8.2	.23	5.9	0.014	0.4	15.5	MW	C	N
0.094	2.39	10782	.50	12.7	.078	2.0	.64	.11	.26	6.6	.17	.74	.09	2.4	0.008	0.2	10.8	BC	C	N
0.094	2.39	1904	.50	12.7	.074	1.9	1.6	.28	.32	8.1	.52	2.3	.18	4.6	0.010	0.3	17.0	MW	C	Z
0.094	2.39	A9-20	.50	12.7	.074	1.9	2.6	.45	.27	6.9	.69	3.1	.13	3.2	0.010	0.3	11.5	MW	C	Z
0.094	2.39	B-403	.50	12.7	.074	1.9	1.8	.31	.33	8.4	.59	2.6	.17	4.3	0.010	0.3	15.8	MW	C	Z
0.094	2.39	B-404	.50	12.7	.070	1.8	3.5	.61	.28	7.1	.97	4.3	.22	5.6	0.012	0.3	17.5	MW	C	Z
0.094	2.39	G-6	.50	12.7	.068	1.7	7.4	1.3	.20	5.2	1.5	6.6	.18	4.5	0.013	0.3	12.5	MW	C	BO
0.094	2.39	B-405	.50	12.7	.066	1.7	6.7	1.2	.23	5.9	1.6	7.0	.27	6.8	0.014	0.4	18.0	MW	C	Z
0.094	2.39	B-406	.50	12.7	.062	1.6	12	2.2	.20	5.0	2.4	11	.30	7.7	0.016	0.4	18.0	MW	C	Z
0.094	2.39	S-860	.53	13.5	.068	1.7	6.1	1.1	.16	4.0	.95	4.2	.18	4.6	0.013	0.3	13.0	SST	C	N
0.094	2.39	B15-14	.53	13.5	.066	1.7	5.8	1.0	.23	5.8	1.3	6.0	.30	7.6	0.014	0.4	20.5	MW	C	N
0.094	2.39	N-101	.53	13.5	.064	1.6	7.4	1.3	.19	4.7	1.4	6.1	.35	8.8	0.015	0.4	22.0	MW	C	Z
0.094	2.39	HH-62	.56	14.3	.078	2.0	.77	.14	.44	11	.34	1.5	.12	3.0	0.008	0.2	14.0	MW	C	GI
0.094	2.39	3066	.56	14.3	.074	1.9	1.7	.29	.39	9.8	.65	2.9	.18	4.4	0.010	0.3	16.5	MW	C	Z
0.094	2.39	B10-14	.56	14.3	.068	1.7	4.0	.70	.27	6.9	1.1	4.9	.29	7.3	0.013	0.3	21.3	MW	C	Z
0.094	2.39	YY-9	.56	14.3	.066	1.7	7.2	1.3	.16	4.2	1.2	5.2	.22	5.7	0.014	0.4	15.0	SST	C	N
0.094	2.39	G-14	.59	15.1	.066	1.7	6.5	1.1	.28	7.2	1.9	8.2	.27	6.9	0.014	0.4	18.5	MW	C	N
0.094	2.39	S-1577	.59	15.1	.054	1.4	63	11	.05	1.2	3.1	14	.20	5.1	0.020	0.5	10.0	SST	CG	N
0.094	2.39	II-10	.63	15.9	.082	2.1	.24	.04	.43	11	.10	.46	.08	2.0	0.006	0.2	12.0	SST	C	N
0.094	2.39	B2-3	.63	15.9	.070	1.8	3.2	.56	.37	9.4	1.2	5.3	.24	6.1	0.012	0.3	19.0	MW	C	N
0.094	2.39	3642	.63	15.9	.066	1.7	9.0	1.6	.21	5.2	1.9	8.2	.21	5.3	0.014	0.4	14.0	MW	C	Z
0.094	2.39	VV-24	.75	19.1	.074	1.9	.94	.16	.47	12	.44	2.0	.26	6.5	0.010					




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.100	2.54	10434	.22	5.6	.086	2.2	.86	.15	.16	4.1	.14	.62	.06	1.4	0.007	0.2	7.00	MW	C	N
0.100	2.54	A9-16	.25	6.4	.082	2.1	2.3	.40	.17	4.4	.39	1.8	.08	1.9	0.009	0.2	7.50	MW	C	N
0.100	2.54	00-41	.31	7.9	.076	1.9	6.3	1.1	.11	2.9	.71	3.2	.11	2.7	0.012	0.3	8.00	SST	C	N
0.100	2.54	10007	.34	8.7	.068	1.7	18	3.1	.13	3.4	2.3	10	.19	4.9	0.016	0.4	11.0	MW	C	N
0.100	2.54	00-25	.38	9.5	.060	1.5	57	10	.05	1.3	2.9	13	.20	5.1	0.020	0.5	9.00	SST	C	N
0.100	2.54	NN-7	.44	11.1	.060	1.5	35	6.1	.08	2.2	2.9	13	.25	6.4	0.020	0.5	11.5	SST	C	N
0.105	2.67	BB-31	.28	7.0	.089	2.3	.86	.15	.20	5.1	.17	.76	.08	1.9	0.008	0.2	8.50	SST	C	N
0.109	2.77	A9-10	.13	3.2	.065	1.7	227	40	.02	.38	3.4	15	.11	2.8	0.022	0.6	4.00	SST	C	N
0.109	2.77	N-17	.16	4.0	.101	2.6	.03	.005	.10	2.6	.003	.01	.05	1.3	0.004	0.1	12.0	SST	C	N
0.109	2.77	EE-23	.17	4.4	.069	1.8	124	22	.03	.84	4.1	18	.11	2.7	0.020	0.5	4.00	MW	C	GI
0.109	2.77	L-71	.19	4.7	.093	2.4	1.1	.20	.12	3.1	.14	.63	.06	1.6	0.008	0.2	7.00	MW	C	N
0.109	2.77	2500	.19	4.8	.089	2.3	3.7	.65	.12	3.0	.44	1.9	.07	1.8	0.010	0.3	6.00	MW	C	Z
0.109	2.77	B15-29	.22	5.6	.091	2.3	1.3	.24	.13	3.3	.17	.77	.09	2.3	0.009	0.2	9.00	MW	C	Z
0.109	2.77	JJ-20	.25	6.4	.093	2.4	.99	.17	.19	4.7	.18	.82	.06	1.6	0.008	0.2	7.00	SST	C	N
0.109	2.77	3722	.25	6.4	.089	2.3	2.5	.43	.16	4.1	.40	1.8	.09	2.3	0.010	0.3	8.00	MW	C	N
0.109	2.77	JJ-1	.25	6.4	.089	2.3	4.3	.74	.09	2.3	.38	1.7	.06	1.5	0.010	0.3	5.00	SST	C	N
0.109	2.77	N-9	.25	6.4	.085	2.2	5.3	.92	.12	3.2	.66	2.9	.10	2.6	0.012	0.3	7.50	SST	C	N
0.109	2.77	V-70	.25	6.4	.081	2.1	5.9	1.0	.05	1.4	.32	1.4	.20	5.0	0.014	0.4	13.0	MW	C	N
0.109	2.77	B-21	.25	6.4	.079	2.0	25	4.4	.05	1.2	1.2	5.3	.09	2.3	0.015	0.4	5.00	SST	C	N
0.109	2.77	O-118	.28	7.1	.091	2.3	1.3	.24	.20	5.1	.27	1.2	.08	2.1	0.009	0.2	9.00	MW	CG	N
0.109	2.77	O-5	.28	7.1	.085	2.2	6.5	1.1	.16	4.0	1.0	4.6	.10	2.4	0.012	0.3	7.00	MW	C	N
0.109	2.77	A15-49	.28	7.1	.073	1.9	33	5.8	.09	2.3	3.0	14	.14	3.7	0.018	0.5	8.00	MW	CG	N
0.109	2.77	QQ-11	.28	7.1	.067	1.7	59	10	.05	1.3	3.1	14	.19	4.8	0.021	0.5	8.00	SST	C	N
0.109	2.77	12527	.30	7.5	.079	2.0	15	2.6	.12	3.1	1.8	8.0	.14	3.4	0.015	0.4	8.00	MW	C	N
0.109	2.77	B15-45	.31	7.9	.095	2.4	.58	.10	.24	6.2	.14	.63	.06	1.4	0.007	0.2	7.00	SST	C	N
0.109	2.77	S-1089	.31	7.9	.091	2.3	1.6	.29	.17	4.4	.28	1.3	.07	1.8	0.009	0.2	7.00	SST	C	N
0.109	2.77	G-16	.31	7.9	.085	2.2	3.2	.55	.17	4.3	.53	2.4	.14	3.7	0.012	0.3	11.0	SST	C	N
0.109	2.77	BB-12	.31	7.9	.083	2.1	5.8	1.0	.14	3.7	.83	3.7	.13	3.3	0.013	0.3	9.00	SST	C	N
0.109	2.77	N-1	.31	7.9	.081	2.1	9.9	1.7	.16	4.1	1.6	7.2	.13	3.4	0.014	0.4	8.50	MW	C	GI
0.109	2.77	12531	.31	7.9	.079	2.0	17.5	3.0	.11	2.8	1.8	8.0	.12	3.0	0.015	0.4	7.00	MW	C	N
0.109	2.77	BB-14	.31	7.9	.069	1.8	50	8.8	.08	2.1	4.1	18	.19	4.8	0.020	0.5	8.50	MW	C	N
0.109	2.77	12454	.34	8.7	.085	2.2	4.8	.85	.14	3.5	.66	2.9	.11	2.7	0.012	0.3	8.00	SST	C	N
0.109	2.77	J-48	.34	8.7	.069	1.8	33	5.7	.08	2.1	2.7	12	.26	6.6	0.020	0.5	12.0	MW	C	N
0.109	2.77	LL-63	.34	8.7	.065	1.7	74	13	.05	1.2	3.6	16	.20	5.0	0.022	0.6	8.00	SST	C	N
0.109	2.77	12534	.34	8.7	.093	2.4	.66	.12	.26	6.6	.17	.77	.08	2.1	0.008	0.2	9.50	SST	C	N
0.109	2.77	00-26	.34	8.7	.073	1.9	22	3.9	.09	2.3	2.0	9.0	.20	5.0	0.018	0.5	10.0	SST	C	N
0.109	2.77	A12-33	.38	9.5	.093	2.4	.71	.13	.29	7.3	.20	.91	.09	2.2	0.008	0.2	10.0	MW	C	N
0.109	2.77	KK-10	.38	9.5	.071	1.8	33	5.7	.07	1.8	2.4	11	.19	4.8	0.019	0.5	9.00	SST	C	N
0.109	2.77	A9-17	.38	9.5	.069	1.8	59	10	.07	1.8	4.1	18	.17	4.3	0.020	0.5	7.50	MW	C	N
0.109	2.77	GG-19	.38	9.5	.069	1.8	23	4.1	.10	2.4	2.2	9.9	.28	7.1	0.020	0.5	14.0	SST	CG	N
0.109	2.77	2937	.41	10.3	.087	2.2	1.8	.31	.24	6.0	.42	1.9	.17	4.3	0.011	0.3	14.5	MW	C	Z
0.109	2.77	1501	.44	11.1	.065	1.7	49	8.5	.11	2.8	5.4	24	.30	7.5	0.022	0.6	12.5	MW	C	Z
0.109	2.77	B2-27	.45	11.5	.077	2.0	9.0	1.6	.20	5.0	1.8	7.9	.26	6.5	0.016	0.4	15.0	MW	C	Z
0.109	2.77	S-829	.47	11.9	.071	1.8	32	5.6	.07	1.9	2.4	11	.19	4.8	0.019	0.5	9.00	SST	C	N
0.109	2.77	L-2	.47	11.9	.069	1.8	27	4.8	.15	3.8	4.1	18	.30	7.6	0.020	0.5	14.0	MW	C	GI
0.109	2.77	N-69	.47	11.9	.065	1.7	57	10	.09	2.4	5.4	24	.26	6.7	0.022	0.6	11.0	MW	C	N
0.109	2.77	V-16	.50	12.7	.089	2.3	.81	.14	.31	7.9	.25	1.1	.19	4.8	0.010	0.3	18.0	SST	C	N
0.109	2.77	B2-33	.50	12.7	.085	2.2	4.4	.76	.24	6.0	1.0	4.6	.13	3.2	0.012	0.3	9.50	MW	C	N
0.109	2.77	S-814	.50	12.7	.063	1.6	51	9.0	.08	2.0	4.1	18	.32	8.0	0.023	0.6	12.8	SST	C	N
0.109	2.77	B-54	.50	12.7	.059	1.5	95	17	.08	1.9	7.2	32	.33	8.3	0.025	0.6	12.0	MW	C	N
0.109	2.77	B15-50	.53	13.5	.087	2.2	2.5	.44	.32	8.2	.80	3.5	.13	3.4	0.011	0.3	11.0	MW	C	N
0.109	2.77	N-19	.53	13.5	.075	1.9	15	2.7	.17	4.3	2.6	11	.22	5.6	0.017	0.4	12.0	MW	C	N
0.109	2.77	L-72	.56	14.3	.095	2.4	.17	.03	.42	11	.07	.31	.14	3.6	0.007	0.2	19.0	SST	C	N
0.109	2.77	N-6	.56	14.3	.093	2.4	.48	.08	.44	11	.21	.94	.12	3.0	0.008	0.2	14.0	MW	C	N
0.109	2.77	AA-37	.56	14.3	.089	2.3	.68	.12	.32	8.2	.22	.98	.24	6.1	0.010	0.3	23.0	MW	C	Z
0.109	2.77	A-38	.59	15.1	.085	2.2	3.0	.52	.35	8.8	1.0	4.6	.17	4.3	0.012	0.3	13.0	MW	C	N
0.109	2.77	U-76	.63	15.9	.085	2.2	2.0	.36	.40	10	.81	3.6	.23	5.8	0.012	0.3	18.0	MW	C	N
0.109	2.77	12529	.63	15.9	.077	2.0	11	1.9	.20	5.2	2.2	9.6	.22	5.7	0.016	0.4	13.0	MW	C	N
0.109	2.77	G-82	.63	15.9	.069	1.8	15	2.6	.18	4.7	2.7	12	.44	11.2	0.020	0.5	21.0	SST	C	N
0.109	2.77	DD-32	.63	15.9	.069	1.8	24	4.2	.17	4.3	4.1	18	.30	7.6	0.020	0.5	15.0	MW	CG	N
0.109	2.77	A9-21	.63	15.9	.067	1.7	29	5.1	.16	4.1	4.7	21	.36	9.1	0.021	0.5	16.0	MW	C	N
0.109	2.77	PP-33	.66	16.7	.081	2.1	2.9	.51	.31	7.8	.90	4.0	.35	8.9	0.014	0.4	24.0	MW	C	Z
0.109	2.77	H-76	.69	17.4	.079	2.0	4.0	.70	.33	8.3	1.3	5.8	.36	9.1	0.015	0.4	24.0	MW	CG	N
0.109	2.77	JJ-57	.75	19.1	.087	2.2	.97	.17	.50	13	.48	2.1	.25	6.4	0.011	0.3	22.0	SST	C	N
0.109	2.77	U-83	.75	19.1	.085	2.2	1.7	.30	.49	12	.84	3.7	.26	6.7	0.012	0.3	21.0	MW	C	Z
0.109	2.77	U-55	.81	20.6	.085	2.2	1.9	.33	.35	8.8	.66	2.9	.22	5.5	0.012	0.3	17.0	SST	C	N
0.109	2.77	A10-37	.84	21.4	.083	2.1	2.3	.40	.36	9.2	.83	3.7	.27	6.9	0.013	0.3	20.0	SST	C	N
0.109	2.77	W-54	.88	22.2	.095	2.4	.19	.03	.74	19	.14	.63	.14	3.6	0.007	0.2	19.0	MW	C	GI
0.109	2.77	MM-47	.88	22.2	.089	2.3	.85	.15	.45	11	.38	1.7	.17	4.3	0.010	0.3	17.0	SST	CG	N
0.109	2.77	KK-5	.94																	





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.114	2.90	GG-7	.16	4.0	.090	2.3	8.1	1.4	.08	2.0	.63	2.8	.07	1.8	0.012	0.3	5.00	SST	C	N
0.114	2.90	00-7	.16	4.0	.070	1.8	192	34	.02	.46	3.5	15	.11	2.8	0.022	0.6	4.00	SST	C	N
0.114	2.90	V-79	.25	6.4	.082	2.1	15	2.6	.07	1.9	1.1	4.8	.18	4.5	0.016	0.4	10.3	MW	C	N
0.114	2.90	10442	.31	7.9	.086	2.2	9.6	1.7	.16	4.1	1.6	6.9	.12	3.1	0.014	0.4	7.75	MW	C	N
0.114	2.90	B12-39	.44	11.1	.074	1.9	30	5.3	.09	2.2	2.6	12	.22	5.6	0.020	0.5	10.0	SST	C	N
0.114	2.90	10909	1.00	25.4	.094	2.4	.91	.16	.63	16	.58	2.6	.17	4.3	0.010	0.3	16.0	MW	C	Z
0.114	2.90	A11-5	1.34	34.1	.068	1.7	12	2.1	.33	8.4	3.9	17	.99	25.1	0.023	0.6	42.0	SST	C	N
0.117	2.97	12747	.27	6.8	.083	2.1	21	3.7	.08	2.0	1.6	7.2	.14	3.5	0.017	0.4	7.00	SST	C	N
0.120	3.05	70109	.19	4.8	.088	2.2	26	4.5	.08	2.0	2.0	8.8	.08	2.1	0.016	0.4	5.25	MW	CG	N
0.120	3.05	70109S	.19	4.8	.088	2.2	22	3.9	.06	1.5	1.3	5.9	.08	2.1	0.016	0.4	5.25	SST	CG	N
0.120	3.05	70131	.19	4.8	.084	2.1	41	7.1	.07	1.7	2.8	12	.10	2.5	0.018	0.5	5.50	MW	CG	N
0.120	3.05	70131S	.19	4.8	.084	2.1	35	6.2	.05	1.3	1.9	8.3	.10	2.5	0.018	0.5	5.50	SST	CG	N
0.120	3.05	70058	.25	6.4	.100	2.5	3.2	.56	.17	4.4	.55	2.4	.05	1.4	0.010	0.3	5.38	MW	CG	N
0.120	3.05	70058S	.25	6.4	.100	2.5	2.8	.49	.13	3.2	.35	1.6	.05	1.4	0.010	0.3	5.38	SST	CG	N
0.120	3.05	70074	.25	6.4	.096	2.4	6.3	1.1	.15	3.8	.94	4.2	.07	1.8	0.012	0.3	5.75	MW	CG	N
0.120	3.05	70074S	.25	6.4	.096	2.4	5.5	.96	.11	2.8	.60	2.7	.07	1.8	0.012	0.3	5.75	SST	CG	N
0.120	3.05	70090	.25	6.4	.092	2.3	11	2.0	.13	3.3	1.5	6.6	.09	2.2	0.014	0.4	6.13	MW	CG	N
0.120	3.05	70090S	.25	6.4	.092	2.3	9.8	1.7	.10	2.5	.94	4.2	.09	2.2	0.014	0.4	6.13	SST	CG	N
0.120	3.05	70110	.25	6.4	.088	2.2	18	3.1	.11	2.9	2.0	8.8	.11	2.7	0.016	0.4	6.75	MW	CG	N
0.120	3.05	70110S	.25	6.4	.088	2.2	15	2.7	.09	2.2	1.3	5.9	.11	2.7	0.016	0.4	6.75	SST	CG	N
0.120	3.05	B3-56	.25	6.4	.088	2.2	15	2.6	.09	2.2	1.3	5.9	.11	2.8	0.016	0.4	6.88	SST	CG	N
0.120	3.05	70132	.25	6.4	.084	2.1	28	5.0	.10	2.5	2.8	12	.13	3.2	0.018	0.5	7.00	MW	CG	N
0.120	3.05	70132S	.25	6.4	.084	2.1	25	4.3	.08	1.9	1.9	8.3	.13	3.2	0.018	0.5	7.00	SST	CG	N
0.120	3.05	70153	.25	6.4	.080	2.0	46	8.1	.08	2.1	3.8	17	.14	3.6	0.020	0.5	7.00	MW	CG	N
0.120	3.05	70153S	.25	6.4	.080	2.0	40	7.0	.06	1.6	2.5	11	.14	3.6	0.020	0.5	7.00	SST	CG	N
0.120	3.05	70171	.25	6.4	.076	1.9	70	12	.07	1.8	5.0	22	.16	4.0	0.022	0.6	7.13	MW	CG	N
0.120	3.05	70171S	.25	6.4	.076	1.9	61	11	.05	1.4	3.3	15	.16	4.0	0.022	0.6	7.13	SST	CG	N
0.120	3.05	70190	.25	6.4	.072	1.8	108	19	.06	1.5	6.4	28	.17	4.3	0.024	0.6	7.00	MW	CG	N
0.120	3.05	70190S	.25	6.4	.072	1.8	94	16	.05	1.1	4.2	19	.17	4.3	0.024	0.6	7.00	SST	CG	N
0.120	3.05	70059	.31	7.9	.100	2.5	2.5	.43	.22	5.7	.55	2.4	.06	1.6	0.010	0.3	6.38	MW	CG	N
0.120	3.05	70059S	.31	7.9	.100	2.5	2.1	.38	.16	4.1	.35	1.6	.06	1.6	0.010	0.3	6.38	SST	CG	N
0.120	3.05	70075	.31	7.9	.096	2.4	5.0	.87	.19	4.8	.94	4.2	.08	2.1	0.012	0.3	6.75	MW	CG	N
0.120	3.05	70075S	.31	7.9	.096	2.4	4.3	.76	.14	3.5	.60	2.7	.08	2.1	0.012	0.3	6.75	SST	CG	N
0.120	3.05	70091	.31	7.9	.092	2.3	8.8	1.5	.17	4.3	1.5	6.6	.10	2.6	0.014	0.4	7.25	MW	CG	N
0.120	3.05	70091S	.31	7.9	.092	2.3	7.7	1.3	.12	3.1	.94	4.2	.10	2.6	0.014	0.4	7.25	SST	CG	N
0.120	3.05	70111	.31	7.9	.088	2.2	14	2.4	.14	3.6	2.0	8.8	.13	3.3	0.016	0.4	8.00	MW	CG	N
0.120	3.05	70111S	.31	7.9	.088	2.2	12	2.1	.11	2.8	1.3	5.9	.13	3.3	0.016	0.4	8.00	SST	CG	N
0.120	3.05	70133	.31	7.9	.084	2.1	22	3.8	.13	3.2	2.8	12	.15	3.9	0.018	0.5	8.50	MW	CG	N
0.120	3.05	70133S	.31	7.9	.084	2.1	19	3.3	.10	2.5	1.9	8.3	.15	3.9	0.018	0.5	8.50	SST	CG	N
0.120	3.05	70154	.31	7.9	.080	2.0	35	6.2	.11	2.7	3.8	17	.17	4.3	0.020	0.5	8.50	MW	CG	N
0.120	3.05	70154S	.31	7.9	.080	2.0	31	5.4	.08	2.1	2.5	11	.17	4.3	0.020	0.5	8.50	SST	CG	N
0.120	3.05	70172	.31	7.9	.076	1.9	54	9.5	.09	2.3	5.0	22	.19	4.8	0.022	0.6	8.63	MW	CG	N
0.120	3.05	70172S	.31	7.9	.076	1.9	47	8.2	.07	1.8	3.3	15	.19	4.8	0.022	0.6	8.63	SST	CG	N
0.120	3.05	70191	.31	7.9	.072	1.8	83	15	.08	1.9	6.4	28	.20	5.2	0.024	0.6	8.50	MW	CG	N
0.120	3.05	70191S	.31	7.9	.072	1.8	72	13	.06	1.5	4.2	19	.20	5.2	0.024	0.6	8.50	SST	CG	N
0.120	3.05	70060	.38	9.7	.100	2.5	2.0	.35	.27	7.0	.55	2.4	.07	1.9	0.010	0.3	7.38	MW	CG	N
0.120	3.05	70060S	.38	9.7	.100	2.5	1.7	.31	.20	5.1	.35	1.6	.07	1.9	0.010	0.3	7.38	SST	CG	N
0.120	3.05	70076	.38	9.7	.096	2.4	4.0	.71	.23	5.9	.94	4.2	.10	2.4	0.012	0.3	7.88	MW	CG	N
0.120	3.05	70076S	.38	9.7	.096	2.4	3.5	.61	.17	4.4	.60	2.7	.10	2.4	0.012	0.3	7.88	SST	CG	N
0.120	3.05	70092	.38	9.7	.092	2.3	7.0	1.2	.21	5.4	1.5	6.6	.12	3.1	0.014	0.4	8.63	MW	CG	N
0.120	3.05	70092S	.38	9.7	.092	2.3	6.1	1.1	.16	3.9	.94	4.2	.12	3.1	0.014	0.4	8.63	SST	CG	N
0.120	3.05	70112	.38	9.7	.088	2.2	11	2.0	.18	4.5	2.0	8.8	.15	3.9	0.016	0.4	9.50	MW	CG	N
0.120	3.05	70112S	.38	9.7	.088	2.2	9.7	1.7	.14	3.5	1.3	5.9	.15	3.9	0.016	0.4	9.50	SST	CG	N
0.120	3.05	70134	.38	9.7	.084	2.1	18	3.2	.15	3.9	2.8	12	.18	4.5	0.018	0.5	9.88	MW	CG	N
0.120	3.05	70134S	.38	9.7	.084	2.1	16	2.7	.12	3.0	1.9	8.3	.18	4.5	0.018	0.5	9.88	SST	CG	N
0.120	3.05	70155	.38	9.7	.080	2.0	28	5.0	.13	3.4	3.8	17	.20	5.2	0.020	0.5	10.1	MW	CG	N
0.120	3.05	70155S	.38	9.7	.080	2.0	25	4.3	.10	2.6	2.5	11	.20	5.2	0.020	0.5	10.1	SST	CG	N
0.120	3.05	70173	.38	9.7	.076	1.9	41	7.3	.12	3.0	5.0	22	.23	5.9	0.022	0.6	10.6	MW	CG	N
0.120	3.05	70173S	.38	9.7	.076	1.9	36	6.3	.09	2.3	3.3	15	.23	5.9	0.022	0.6	10.6	SST	CG	N
0.120	3.05	70192	.38	9.7	.072	1.8	65	11	.10	2.5	6.4	28	.25	6.2	0.024	0.6	10.3	MW	CG	N
0.120	3.05	70192S	.38	9.7	.072	1.8	57	9.9	.07	1.9	4.2	19	.25	6.2	0.024	0.6	10.3	SST	CG	N
0.120	3.05	B3-57	.44	11.1	.092	2.3	5.8	1.0	.26	6.5	1.5	6.6	.14	3.6	0.014	0.4	10.0	MW	CG	N
0.120	3.05	70061	.44	11.2	.100	2.5	1.7	.30	.32	8.2	.55	2.4	.08	2.1	0.010	0.3	8.38	MW	CG	N
0.120	3.05	70061S	.44	11.2	.100	2.5	1.5	.26	.24	6.0	.35	1.6	.08	2.1	0.010	0.3	8.38	SST	CG	N
0.120	3.05	70077	.44	11.2	.096	2.4	3.4	.59	.28	7.1	.94	4.2	.11	2.7	0.012	0.3	9.00	MW	CG	N
0.120	3.05	70077S	.44	11.2	.096	2.4	2.9	.51	.20	5.2	.60	2.7	.11	2.7	0.012	0.3	9.00	SST	CG	N
0.120	3.05	70093	.44	11.2	.092	2.3	6.0	1.0	.25	6.3	1.5	6.6	.14	3.5	0.014	0.4	9.75	MW	CG	N
0.120	3.05	70093S	.44	11.2	.092	2.3	5.2	.91	.18	4.6	.94	4.2	.14	3.5	0.014	0.4	9.75	SST	CG	N
0.120	3.05	70113	.44	11.2	.088	2.2	9.4	1.7	.21	5.3	2.0	8.8	.17	4.4	0.016	0.4	10.9	MW	CG	N




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.120	3.05	70078	.50	12.7	.096	2.4	3.0	.53	.31	8.0	.94	4.2	.12	3.0	0.012	0.3	9.88	MW	CG	N
0.120	3.05	70078S	.50	12.7	.096	2.4	2.6	.46	.23	5.8	.60	2.7	.12	3.0	0.012	0.3	9.88	SST	CG	N
0.120	3.05	70094	.50	12.7	.092	2.3	5.2	.91	.28	7.2	1.5	6.6	.15	3.9	0.014	0.4	10.9	MW	CG	N
0.120	3.05	70094S	.50	12.7	.092	2.3	4.5	.80	.21	5.3	.94	4.2	.15	3.9	0.014	0.4	10.9	SST	CG	N
0.120	3.05	70114	.50	12.7	.088	2.2	8.4	1.5	.24	6.0	2.0	8.8	.19	4.9	0.016	0.4	12.0	MW	CG	N
0.120	3.05	70114S	.50	12.7	.088	2.2	7.3	1.3	.18	4.6	1.3	5.9	.19	4.9	0.016	0.4	12.0	SST	CG	N
0.120	3.05	70136	.50	12.7	.084	2.1	13	2.3	.21	5.4	2.8	12	.23	5.9	0.018	0.5	12.9	MW	CG	N
0.120	3.05	70136S	.50	12.7	.084	2.1	11	2.0	.16	4.1	1.9	8.3	.23	5.9	0.018	0.5	12.9	SST	CG	N
0.120	3.05	70157	.50	12.7	.080	2.0	21	3.7	.18	4.6	3.8	17	.26	6.6	0.020	0.5	13.0	MW	CG	N
0.120	3.05	70157S	.50	12.7	.080	2.0	18	3.2	.14	3.5	2.5	11	.26	6.6	0.020	0.5	13.0	SST	CG	N
0.120	3.05	70175	.50	12.7	.076	1.9	31	5.4	.16	4.1	5.0	22	.30	7.5	0.022	0.6	13.5	MW	CG	N
0.120	3.05	70175S	.50	12.7	.076	1.9	27	4.7	.12	3.1	3.3	15	.30	7.5	0.022	0.6	13.5	SST	CG	N
0.120	3.05	70194	.50	12.7	.072	1.8	48	8.4	.13	3.4	6.4	28	.32	8.1	0.024	0.6	13.3	MW	CG	N
0.120	3.05	70194S	.50	12.7	.072	1.8	42	7.3	.10	2.6	4.2	19	.32	8.1	0.024	0.6	13.3	SST	CG	N
0.120	3.05	70063	.56	14.2	.100	2.5	1.4	.24	.39	10	.55	2.4	.10	2.5	0.010	0.3	9.75	MW	CG	N
0.120	3.05	70063S	.56	14.2	.100	2.5	1.2	.21	.29	7.3	.35	1.6	.10	2.5	0.010	0.3	9.75	SST	CG	N
0.120	3.05	70079	.56	14.2	.096	2.4	2.6	.45	.36	9.2	.94	4.2	.13	3.4	0.012	0.3	11.1	MW	CG	N
0.120	3.05	70079S	.56	14.2	.096	2.4	2.3	.39	.27	6.8	.60	2.7	.13	3.4	0.012	0.3	11.1	SST	CG	N
0.120	3.05	70095	.56	14.2	.092	2.3	4.6	.80	.32	8.2	1.5	6.6	.17	4.3	0.014	0.4	12.1	MW	CG	N
0.120	3.05	70095S	.56	14.2	.092	2.3	4.0	.70	.24	6.0	.94	4.2	.17	4.3	0.014	0.4	12.1	SST	CG	N
0.120	3.05	70115	.56	14.2	.088	2.2	7.4	1.3	.27	6.8	2.0	8.8	.21	5.4	0.016	0.4	13.4	MW	CG	N
0.120	3.05	70115S	.56	14.2	.088	2.2	6.4	1.1	.21	5.2	1.3	5.9	.21	5.4	0.016	0.4	13.4	SST	CG	N
0.120	3.05	70137	.56	14.2	.084	2.1	11	2.0	.24	6.2	2.8	12	.26	6.6	0.018	0.5	14.4	MW	CG	N
0.120	3.05	70137S	.56	14.2	.084	2.1	10	1.7	.19	4.7	1.9	8.3	.26	6.6	0.018	0.5	14.4	SST	CG	N
0.120	3.05	70158	.56	14.2	.080	2.0	18	3.2	.21	5.3	3.8	17	.29	7.4	0.020	0.5	14.6	MW	CG	N
0.120	3.05	70158S	.56	14.2	.080	2.0	16	2.8	.16	4.0	2.5	11	.29	7.4	0.020	0.5	14.6	SST	CG	N
0.120	3.05	70176	.56	14.2	.076	1.9	28	4.9	.18	4.5	5.0	22	.33	8.3	0.022	0.6	14.8	MW	CG	N
0.120	3.05	70176S	.56	14.2	.076	1.9	24	4.3	.14	3.4	3.3	15	.33	8.3	0.022	0.6	14.8	SST	CG	N
0.120	3.05	70195	.56	14.2	.072	1.8	42	7.4	.15	3.8	6.4	28	.35	9.0	0.024	0.6	14.8	MW	CG	N
0.120	3.05	70195S	.56	14.2	.072	1.8	37	6.4	.12	2.9	4.2	19	.35	9.0	0.024	0.6	14.8	SST	CG	N
0.120	3.05	70064	.63	16.0	.100	2.5	1.2	.21	.46	12	.55	2.4	.11	2.8	0.010	0.3	11.0	MW	CG	N
0.120	3.05	70064S	.63	16.0	.100	2.5	1.0	.18	.34	8.5	.35	1.6	.11	2.8	0.010	0.3	11.0	SST	CG	N
0.120	3.05	70080	.63	16.0	.096	2.4	2.4	.42	.39	10	.94	4.2	.14	3.6	0.012	0.3	11.9	MW	CG	N
0.120	3.05	70080S	.63	16.0	.096	2.4	2.1	.36	.29	7.3	.60	2.7	.14	3.6	0.012	0.3	11.9	SST	CG	N
0.120	3.05	70096	.63	16.0	.092	2.3	4.1	.72	.36	9.1	1.5	6.6	.19	4.7	0.014	0.4	13.3	MW	CG	N
0.120	3.05	70096S	.63	16.0	.092	2.3	3.6	.63	.26	6.7	.94	4.2	.19	4.7	0.014	0.4	13.3	SST	CG	N
0.120	3.05	70116	.63	16.0	.088	2.2	6.6	1.2	.30	7.7	2.0	8.8	.24	6.0	0.016	0.4	14.8	MW	CG	N
0.120	3.05	70116S	.63	16.0	.088	2.2	5.7	1.0	.23	5.9	1.3	5.9	.24	6.0	0.016	0.4	14.8	SST	CG	N
0.120	3.05	70138	.63	16.0	.084	2.1	11	1.9	.26	6.6	2.8	12	.27	6.9	0.018	0.5	15.1	MW	CG	N
0.120	3.05	70138S	.63	16.0	.084	2.1	9.4	1.6	.20	5.0	1.9	8.3	.27	6.9	0.018	0.5	15.1	SST	CG	N
0.120	3.05	70159	.63	16.0	.080	2.0	16	2.9	.23	5.9	3.8	17	.32	8.2	0.020	0.5	16.1	MW	CG	N
0.120	3.05	70159S	.63	16.0	.080	2.0	14	2.5	.18	4.5	2.5	11	.32	8.2	0.020	0.5	16.1	SST	CG	N
0.120	3.05	70177	.63	16.0	.076	1.9	25	4.4	.20	5.1	5.0	22	.36	9.1	0.022	0.6	16.4	MW	CG	N
0.120	3.05	70177S	.63	16.0	.076	1.9	22	3.8	.15	3.9	3.3	15	.36	9.1	0.022	0.6	16.4	SST	CG	N
0.120	3.05	70196	.63	16.0	.072	1.8	38	6.6	.17	4.3	6.4	28	.39	10.0	0.024	0.6	16.4	MW	CG	N
0.120	3.05	70196S	.63	16.0	.072	1.8	33	5.7	.13	3.3	4.2	19	.39	10.0	0.024	0.6	16.4	SST	CG	N
0.120	3.05	70065	.69	17.5	.100	2.5	1.1	.19	.50	13	.55	2.4	.12	3.0	0.010	0.3	11.9	MW	CG	N
0.120	3.05	70065S	.69	17.5	.100	2.5	.95	.17	.37	9.4	.35	1.6	.12	3.0	0.010	0.3	11.9	SST	CG	N
0.120	3.05	70081	.69	17.5	.096	2.4	2.1	.37	.45	11	.94	4.2	.16	4.0	0.012	0.3	13.3	MW	CG	N
0.120	3.05	70081S	.69	17.5	.096	2.4	1.8	.32	.33	8.3	.60	2.7	.16	4.0	0.012	0.3	13.3	SST	CG	N
0.120	3.05	70097	.69	17.5	.092	2.3	3.7	.66	.40	10	1.5	6.6	.20	5.1	0.014	0.4	14.4	MW	CG	N
0.120	3.05	70097S	.69	17.5	.092	2.3	3.3	.57	.29	7.4	.94	4.2	.20	5.1	0.014	0.4	14.4	SST	CG	N
0.120	3.05	70117	.69	17.5	.088	2.2	5.9	1.0	.34	8.6	2.0	8.8	.26	6.6	0.016	0.4	16.3	MW	CG	N
0.120	3.05	70117S	.69	17.5	.088	2.2	5.1	.90	.26	6.6	1.3	5.9	.26	6.6	0.016	0.4	16.3	SST	CG	N
0.120	3.05	70139	.69	17.5	.084	2.1	9.4	1.6	.30	7.5	2.8	12	.31	7.8	0.018	0.5	17.1	MW	CG	N
0.120	3.05	70139S	.69	17.5	.084	2.1	8.2	1.4	.23	5.8	1.9	8.3	.31	7.8	0.018	0.5	17.1	SST	CG	N
0.120	3.05	70160	.69	17.5	.080	2.0	15	2.6	.26	6.5	3.8	17	.35	9.0	0.020	0.5	17.6	MW	CG	N
0.120	3.05	70160S	.69	17.5	.080	2.0	13	2.2	.20	5.0	2.5	11	.35	9.0	0.020	0.5	17.6	SST	CG	N
0.120	3.05	70178	.69	17.5	.076	1.9	22	3.8	.23	5.9	5.0	22	.41	10.4	0.022	0.6	18.6	MW	CG	N
0.120	3.05	70178S	.69	17.5	.076	1.9	19	3.3	.18	4.5	3.3	15	.41	10.4	0.022	0.6	18.6	SST	CG	N
0.120	3.05	70197	.69	17.5	.072	1.8	34	5.9	.19	4.8	6.4	28	.43	11.0	0.024	0.6	18.0	MW	CG	N
0.120	3.05	70197S	.69	17.5	.072	1.8	29	5.1	.14	3.7	4.2	19	.43	11.0	0.024	0.6	18.0	SST	CG	N
0.120	3.05	70066	.75	19.1	.100	2.5	1.0	.18	.55	14	.55	2.4	.13	3.3	0.010	0.3	12.8	MW	CG	N
0.120	3.05	70066S	.75	19.1	.100	2.5	.87	.15	.40	10	.35	1.6	.13	3.3	0.010	0.3	12.8	SST	CG	N
0.120	3.05	70082	.75	19.1	.096	2.4	2.0	.35	.47	12	.94	4.2	.17	4.2	0.012	0.3	13.9	MW	CG	N
0.120	3.05	70082S	.75	19.1	.096	2.4	1.7	.30	.35	8.8	.60	2.7	.17	4.2	0.012	0.3	13.9	SST	CG	N
0.120	3.05	70098	.75	19.1	.092	2.3	3.4	.60	.44	11	1.5	6.6	.22	5.6	0.014	0.4	15.6	MW	CG	N
0.120	3.05	70098S	.75	19.1	.092	2.3	3.0	.52	.32	8.1	.94	4.2	.22	5.6	0.014	0.4				




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.120	3.05	70083	.81	20.6	.096	2.4	1.8	.32	.52	13	.94	4.2	.18	4.6	0.012	0.3	15.1	MW	CG	N
0.120	3.05	70083S	.81	20.6	.096	2.4	1.6	.27	.38	9.7	.60	2.7	.18	4.6	0.012	0.3	15.1	SST	CG	N
0.120	3.05	70099	.81	20.6	.092	2.3	3.1	.54	.48	12	1.5	6.6	.24	6.0	0.014	0.4	17.0	MW	CG	N
0.120	3.05	70099S	.81	20.6	.092	2.3	2.7	.47	.35	8.9	.94	4.2	.24	6.0	0.014	0.4	17.0	SST	CG	N
0.120	3.05	70120	.81	20.6	.088	2.2	5.0	.88	.40	10	2.0	8.8	.30	7.6	0.016	0.4	18.8	MW	CG	N
0.120	3.05	70120S	.81	20.6	.088	2.2	4.3	.76	.30	7.7	1.3	5.9	.30	7.6	0.016	0.4	18.8	SST	CG	N
0.120	3.05	70142	.81	20.6	.084	2.1	7.9	1.4	.35	9.0	2.8	12	.36	9.1	0.018	0.5	20.0	MW	CG	N
0.120	3.05	70142S	.81	20.6	.084	2.1	6.9	1.2	.27	6.9	1.9	8.3	.36	9.1	0.018	0.5	20.0	SST	CG	N
0.120	3.05	70162	.81	20.6	.080	2.0	12	2.2	.31	7.8	3.8	17	.41	10.5	0.020	0.5	20.6	MW	CG	N
0.120	3.05	70162S	.81	20.6	.080	2.0	11	1.9	.23	6.0	2.5	11	.41	10.5	0.020	0.5	20.6	SST	CG	N
0.120	3.05	70180	.81	20.6	.076	1.9	18	3.2	.27	6.9	5.0	22	.47	12.0	0.022	0.6	21.5	MW	CG	N
0.120	3.05	70180S	.81	20.6	.076	1.9	16	2.8	.21	5.3	3.3	15	.47	12.0	0.022	0.6	21.5	SST	CG	N
0.120	3.05	70199	.81	20.6	.072	1.8	28	5.0	.22	5.7	6.4	28	.50	12.8	0.024	0.6	21.0	MW	CG	N
0.120	3.05	70199S	.81	20.6	.072	1.8	25	4.3	.17	4.4	4.2	19	.50	12.8	0.024	0.6	21.0	SST	CG	N
0.120	3.05	70068	.88	22.4	.100	2.5	.90	.16	.61	16	.55	2.4	.14	3.6	0.010	0.3	14.0	MW	CG	N
0.120	3.05	70068S	.88	22.4	.100	2.5	.78	.14	.45	11	.35	1.6	.14	3.6	0.010	0.3	14.0	SST	CG	N
0.120	3.05	70084	.88	22.4	.096	2.4	1.7	.30	.55	14	.94	4.2	.19	4.9	0.012	0.3	15.9	MW	CG	N
0.120	3.05	70084S	.88	22.4	.096	2.4	1.5	.26	.40	10	.60	2.7	.19	4.9	0.012	0.3	15.9	SST	CG	N
0.120	3.05	70100	.88	22.4	.092	2.3	2.9	.51	.51	13	1.5	6.6	.25	6.4	0.014	0.4	18.0	MW	CG	N
0.120	3.05	70100S	.88	22.4	.092	2.3	2.5	.44	.37	9.5	.94	4.2	.25	6.4	0.014	0.4	18.0	SST	CG	N
0.120	3.05	70122	.88	22.4	.088	2.2	4.6	.80	.43	11	2.0	8.8	.32	8.2	0.016	0.4	20.3	MW	CG	N
0.120	3.05	70122S	.88	22.4	.088	2.2	4.0	.70	.33	8.4	1.3	5.9	.32	8.2	0.016	0.4	20.3	SST	CG	N
0.120	3.05	70144	.88	22.4	.084	2.1	7.3	1.3	.38	9.7	2.8	12	.39	9.8	0.018	0.5	21.5	MW	CG	N
0.120	3.05	70144S	.88	22.4	.084	2.1	6.3	1.1	.29	7.4	1.9	8.3	.39	9.8	0.018	0.5	21.5	SST	CG	N
0.120	3.05	70163	.88	22.4	.080	2.0	11	2.0	.34	8.6	3.8	17	.45	11.4	0.020	0.5	22.5	MW	CG	N
0.120	3.05	70163S	.88	22.4	.080	2.0	9.8	1.7	.26	6.6	2.5	11	.45	11.4	0.020	0.5	22.5	SST	CG	N
0.120	3.05	70182	.88	22.4	.076	1.9	17	3.0	.29	7.4	5.0	22	.50	12.8	0.022	0.6	22.9	MW	CG	N
0.120	3.05	70182S	.88	22.4	.076	1.9	15	2.6	.22	5.6	3.3	15	.50	12.8	0.022	0.6	22.9	SST	CG	N
0.120	3.05	70200	.88	22.4	.072	1.8	26	4.5	.24	6.2	6.4	28	.55	13.9	0.024	0.6	22.8	MW	CG	N
0.120	3.05	70200S	.88	22.4	.072	1.8	23	4.0	.19	4.8	4.2	19	.55	13.9	0.024	0.6	22.8	SST	CG	N
0.120	3.05	70101	.91	23.1	.092	2.3	8.6	1.5	.17	4.4	1.5	6.6	.10	2.6	0.014	0.4	7.38	MW	CG	N
0.120	3.05	70101S	.91	23.1	.092	2.3	7.5	1.3	.13	3.2	.94	4.2	.10	2.6	0.014	0.4	7.38	SST	CG	N
0.120	3.05	70069	.94	23.9	.100	2.5	.80	.14	.69	17	.55	2.4	.16	3.9	0.010	0.3	15.5	MW	CG	N
0.120	3.05	70069S	.94	23.9	.100	2.5	.70	.12	.50	13	.35	1.6	.16	3.9	0.010	0.3	15.5	SST	CG	N
0.120	3.05	70085	.94	23.9	.096	2.4	1.5	.26	.63	16	.94	4.2	.21	5.4	0.012	0.3	17.8	MW	CG	N
0.120	3.05	70085S	.94	23.9	.096	2.4	1.3	.23	.46	12	.60	2.7	.21	5.4	0.012	0.3	17.8	SST	CG	N
0.120	3.05	70102	.94	23.9	.092	2.3	2.7	.47	.55	14	1.5	6.6	.27	6.8	0.014	0.4	19.1	MW	CG	N
0.120	3.05	70102S	.94	23.9	.092	2.3	2.4	.41	.40	10	.94	4.2	.27	6.8	0.014	0.4	19.1	SST	CG	N
0.120	3.05	70124	.94	23.9	.088	2.2	4.3	.75	.46	12	2.0	8.8	.34	8.7	0.016	0.4	21.5	MW	CG	N
0.120	3.05	70124S	.94	23.9	.088	2.2	3.7	.65	.35	9.0	1.3	5.9	.34	8.7	0.016	0.4	21.5	SST	CG	N
0.120	3.05	70146	.94	23.9	.084	2.1	6.8	1.2	.41	10	2.8	12	.41	10.5	0.018	0.5	22.9	MW	CG	N
0.120	3.05	70146S	.94	23.9	.084	2.1	5.9	1.0	.31	8.0	1.9	8.3	.41	10.5	0.018	0.5	22.9	SST	CG	N
0.120	3.05	70164	.94	23.9	.080	2.0	11	1.9	.36	9.1	3.8	17	.48	12.1	0.020	0.5	23.8	MW	CG	N
0.120	3.05	70164S	.94	23.9	.080	2.0	9.2	1.6	.27	7.0	2.5	11	.48	12.1	0.020	0.5	23.8	SST	CG	N
0.120	3.05	70183	.94	23.9	.076	1.9	16	2.8	.31	8.0	5.0	22	.54	13.8	0.022	0.6	24.6	MW	CG	N
0.120	3.05	70183S	.94	23.9	.076	1.9	14	2.4	.24	6.1	3.3	15	.54	13.8	0.022	0.6	24.6	SST	CG	N
0.120	3.05	70201	.94	23.9	.072	1.8	24	4.3	.26	6.6	6.4	28	.58	14.7	0.024	0.6	24.1	MW	CG	N
0.120	3.05	70201S	.94	23.9	.072	1.8	21	3.7	.20	5.1	4.2	19	.58	14.7	0.024	0.6	24.1	SST	CG	N
0.120	3.05	70070	1.00	25.4	.100	2.5	.70	.12	.78	20	.55	2.4	.17	4.4	0.010	0.3	17.4	MW	CG	N
0.120	3.05	70070S	1.00	25.4	.100	2.5	.61	.11	.57	15	.35	1.6	.17	4.4	0.010	0.3	17.4	SST	CG	N
0.120	3.05	70086	1.00	25.4	.096	2.4	1.5	.26	.63	16	.94	4.2	.21	5.4	0.012	0.3	17.8	MW	CG	N
0.120	3.05	70086S	1.00	25.4	.096	2.4	1.3	.23	.46	12	.60	2.7	.21	5.4	0.012	0.3	17.8	SST	CG	N
0.120	3.05	70103	1.00	25.4	.092	2.3	2.5	.44	.59	15	1.5	6.6	.29	7.3	0.014	0.4	20.5	MW	CG	N
0.120	3.05	70103S	1.00	25.4	.092	2.3	2.2	.38	.43	11	.94	4.2	.29	7.3	0.014	0.4	20.5	SST	CG	N
0.120	3.05	70125	1.00	25.4	.088	2.2	4.1	.71	.49	12	2.0	8.8	.36	9.2	0.016	0.4	22.6	MW	CG	N
0.120	3.05	70125S	1.00	25.4	.088	2.2	3.5	.62	.37	9.5	1.3	5.9	.36	9.2	0.016	0.4	22.6	SST	CG	N
0.120	3.05	70147	1.00	25.4	.084	2.1	6.4	1.1	.44	11	2.8	12	.44	11.1	0.018	0.5	24.3	MW	CG	N
0.120	3.05	70147S	1.00	25.4	.084	2.1	5.6	.97	.33	8.5	1.9	8.3	.44	11.1	0.018	0.5	24.3	SST	CG	N
0.120	3.05	70165	1.00	25.4	.080	2.0	9.9	1.7	.38	9.7	3.8	17	.51	12.8	0.020	0.5	25.3	MW	CG	N
0.120	3.05	70165S	1.00	25.4	.080	2.0	8.6	1.5	.29	7.4	2.5	11	.51	12.8	0.020	0.5	25.3	SST	CG	N
0.120	3.05	70184	1.00	25.4	.076	1.9	15	2.6	.34	8.5	5.0	22	.58	14.6	0.022	0.6	26.1	MW	CG	N
0.120	3.05	70184S	1.00	25.4	.076	1.9	13	2.3	.26	6.5	3.3	15	.58	14.6	0.022	0.6	26.1	SST	CG	N
0.120	3.05	70202	1.00	25.4	.072	1.8	23	4.0	.28	7.1	6.4	28	.62	15.7	0.024	0.6	25.8	MW	CG	N
0.120	3.05	70202S	1.00	25.4	.072	1.8	20	3.5	.21	5.4	4.2	19	.62	15.7	0.024	0.6	25.8	SST	CG	N
0.120	3.05	70071	1.13	28.7	.100	2.5	.70	.12	.78	20	.55	2.4	.17	4.4	0.010	0.3	17.4	MW	CG	N
0.120	3.05	70071S	1.13	28.7	.100	2.5	.61	.11	.57	15	.35	1.6	.17	4.4	0.010	0.3	17.4	SST	CG	N
0.120	3.05	70087	1.13	28.7	.096	2.4	1.3	.23	.73	18	.94	4.2	.24	6.2	0.012	0.3	20.3	MW	CG	N
0.120	3.05	70087S	1.13	28.7	.096	2.4	1.1	.20	.53	14	.60	2.7	.24	6.2	0.012	0.3	20.3	SST	CG	N




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.120	3.05	70072	1.25	31.8	.100	2.5	.60	.11	.92	23	.55	2.4	.20	5.1	0.010	0.3	20.0	MW	CG	N
0.120	3.05	70072S	1.25	31.8	.100	2.5	.52	.09	.67	17	.35	1.6	.20	5.1	0.010	0.3	20.0	SST	CG	N
0.120	3.05	70088	1.25	31.8	.096	2.4	1.2	.21	.79	20	.94	4.2	.26	6.6	0.012	0.3	21.8	MW	CG	N
0.120	3.05	70088S	1.25	31.8	.096	2.4	1.0	.18	.58	15	.60	2.7	.26	6.6	0.012	0.3	21.8	SST	CG	N
0.120	3.05	70105	1.25	31.8	.092	2.3	2.0	.35	.74	19	1.5	6.6	.35	8.9	0.014	0.4	25.1	MW	CG	N
0.120	3.05	70105S	1.25	31.8	.092	2.3	1.7	.31	.54	14	.94	4.2	.35	8.9	0.014	0.4	25.1	SST	CG	N
0.120	3.05	70127	1.25	31.8	.088	2.2	3.2	.56	.62	16	2.0	8.8	.45	11.4	0.016	0.4	28.1	MW	CG	N
0.120	3.05	70127S	1.25	31.8	.088	2.2	2.8	.49	.47	12	1.3	5.9	.45	11.4	0.016	0.4	28.1	SST	CG	N
0.120	3.05	70149	1.25	31.8	.084	2.1	5.1	.89	.55	14	2.8	12	.54	13.8	0.018	0.5	30.1	MW	CG	N
0.120	3.05	70149S	1.25	31.8	.084	2.1	4.4	.77	.42	11	1.9	8.3	.54	13.8	0.018	0.5	30.1	SST	CG	N
0.120	3.05	70167	1.25	31.8	.080	2.0	7.9	1.4	.48	12	3.8	17	.62	15.8	0.020	0.5	31.1	MW	CG	N
0.120	3.05	70167S	1.25	31.8	.080	2.0	6.9	1.2	.37	9.3	2.5	11	.62	15.8	0.020	0.5	31.1	SST	CG	N
0.120	3.05	70186	1.25	31.8	.076	1.9	12	2.1	.42	11	5.0	22	.72	18.2	0.022	0.6	32.5	MW	CG	N
0.120	3.05	70186S	1.25	31.8	.076	1.9	10	1.8	.32	8.2	3.3	15	.72	18.2	0.022	0.6	32.5	SST	CG	N
0.120	3.05	70204	1.25	31.8	.072	1.8	18	3.1	.35	9.0	6.4	28	.77	19.5	0.024	0.6	32.0	MW	CG	N
0.120	3.05	70204S	1.25	31.8	.072	1.8	16	2.7	.27	6.9	4.2	19	.77	19.5	0.024	0.6	32.0	SST	CG	N
0.120	3.05	70107	1.38	35.1	.092	2.3	1.8	.32	.82	21	1.5	6.6	.39	9.9	0.014	0.4	27.8	MW	CG	N
0.120	3.05	70107S	1.38	35.1	.092	2.3	1.6	.27	.60	15	.94	4.2	.39	9.9	0.014	0.4	27.8	SST	CG	N
0.120	3.05	70129	1.38	35.1	.088	2.2	2.9	.51	.68	17	2.0	8.8	.49	12.5	0.016	0.4	30.9	MW	CG	N
0.120	3.05	70129S	1.38	35.1	.088	2.2	2.5	.44	.52	13	1.3	5.9	.49	12.5	0.016	0.4	30.9	SST	CG	N
0.120	3.05	70151	1.38	35.1	.084	2.1	4.6	.81	.61	15	2.8	12	.59	15.0	0.018	0.5	32.9	MW	CG	N
0.120	3.05	70151S	1.38	35.1	.084	2.1	4.0	.70	.46	12	1.9	8.3	.59	15.0	0.018	0.5	32.9	SST	CG	N
0.120	3.05	70169	1.38	35.1	.080	2.0	7.0	1.2	.54	14	3.8	17	.70	17.7	0.020	0.5	34.9	MW	CG	N
0.120	3.05	70169S	1.38	35.1	.080	2.0	6.1	1.1	.41	11	2.5	11	.70	17.7	0.020	0.5	34.9	SST	CG	N
0.120	3.05	70188	1.38	35.1	.076	1.9	11	1.9	.47	12	5.0	22	.78	19.8	0.022	0.6	35.5	MW	CG	N
0.120	3.05	70188S	1.38	35.1	.076	1.9	9.3	1.6	.36	9.0	3.3	15	.78	19.8	0.022	0.6	35.5	SST	CG	N
0.120	3.05	70073	1.50	38.1	.100	2.5	.50	.09	1.1	28	.55	2.4	.24	6.0	0.010	0.3	23.6	MW	CG	N
0.120	3.05	70073S	1.50	38.1	.100	2.5	.43	.08	.81	20	.35	1.6	.24	6.0	0.010	0.3	23.6	SST	CG	N
0.120	3.05	70089	1.50	38.1	.096	2.4	1.0	.18	.94	24	.94	4.2	.31	7.8	0.012	0.3	25.6	MW	CG	N
0.120	3.05	70089S	1.50	38.1	.096	2.4	.87	.15	.69	17	.60	2.7	.31	7.8	0.012	0.3	25.6	SST	CG	N
0.120	3.05	70108	1.50	38.1	.092	2.3	1.7	.30	.85	22	1.5	6.6	.40	10.2	0.014	0.4	28.8	MW	CG	N
0.120	3.05	70108S	1.50	38.1	.092	2.3	1.5	.26	.63	16	.94	4.2	.40	10.2	0.014	0.4	28.8	SST	CG	N
0.120	3.05	70130	1.50	38.1	.088	2.2	2.7	.48	.72	18	2.0	8.8	.52	13.2	0.016	0.4	32.5	MW	CG	N
0.120	3.05	70130S	1.50	38.1	.088	2.2	2.4	.42	.55	14	1.3	5.9	.52	13.2	0.016	0.4	32.5	SST	CG	N
0.120	3.05	70152	1.50	38.1	.084	2.1	4.2	.73	.67	17	2.8	12	.65	16.6	0.018	0.5	36.3	MW	CG	N
0.120	3.05	70152S	1.50	38.1	.084	2.1	3.6	.63	.51	13	1.9	8.3	.65	16.6	0.018	0.5	36.3	SST	CG	N
0.120	3.05	70170	1.50	38.1	.080	2.0	6.5	1.1	.59	15	3.8	17	.75	19.1	0.020	0.5	37.6	MW	CG	N
0.120	3.05	70170S	1.50	38.1	.080	2.0	5.6	.98	.45	11	2.5	11	.75	19.1	0.020	0.5	37.6	SST	CG	N
0.120	3.05	70189	1.50	38.1	.076	1.9	9.7	1.7	.51	13	5.0	22	.86	21.7	0.022	0.6	38.9	MW	CG	N
0.120	3.05	70189S	1.50	38.1	.076	1.9	8.4	1.5	.39	10	3.3	15	.86	21.7	0.022	0.6	38.9	SST	CG	N
0.120	3.05	70205	1.50	38.1	.072	1.8	15	2.6	.43	11	6.4	28	.92	23.2	0.024	0.6	38.1	MW	CG	N
0.120	3.05	70205S	1.50	38.1	.072	1.8	13	2.3	.33	8.3	4.2	19	.92	23.2	0.024	0.6	38.1	SST	CG	N
0.125	3.18	DD-65	.13	3.2	.105	2.7	3.2	.55	.08	1.9	.24	1.1	.05	1.3	0.010	0.3	5.00	MW	CG	GI
0.125	3.18	10195	.13	3.2	.095	2.4	36	6.4	.04	1.1	1.6	7.0	.07	1.7	0.015	0.4	3.50	MW	C	N
0.125	3.18	LL-57	.16	4.0	.085	2.2	99	17	.04	.93	3.7	16	.10	2.5	0.020	0.5	4.00	MW	C	N
0.125	3.18	DD-57	.19	4.8	.095	2.4	11	1.9	.08	1.9	.81	3.6	.11	2.9	0.015	0.4	6.50	SST	C	N
0.125	3.18	B14-3	.19	4.8	.087	2.2	52	9.2	.06	1.5	3.2	14	.11	2.9	0.019	0.5	5.00	MW	C	N
0.125	3.18	B-83	.19	4.8	.085	2.2	66	12	.06	1.4	3.7	16	.12	3.0	0.020	0.5	5.00	MW	C	N
0.125	3.18	N-4	.22	5.6	.111	2.8	.35	.06	.16	4.0	.05	.24	.06	1.6	0.007	0.2	8.00	MW	C	N
0.125	3.18	S-1576	.22	5.6	.109	2.8	.65	.11	.16	3.9	.10	.45	.06	1.6	0.008	0.2	7.00	SST	C	N
0.125	3.18	B15-7	.22	5.6	.104	2.6	1.9	.34	.12	3.2	.24	1.1	.09	2.4	0.011	0.3	8.00	MW	C	N
0.125	3.18	DD-1	.22	5.6	.097	2.5	6.5	1.1	.10	2.5	.65	2.9	.12	3.0	0.014	0.4	7.50	SST	C	N
0.125	3.18	MM-80	.22	5.6	.097	2.5	10	1.8	.09	2.3	.91	4.0	.09	2.3	0.014	0.4	5.50	SST	C	N
0.125	3.18	B7-3	.22	5.6	.097	2.5	13	2.4	.11	2.7	1.4	6.3	.08	2.1	0.014	0.4	5.00	MW	C	N
0.125	3.18	A10-4	.22	5.6	.075	1.9	112	20	.04	1.1	4.9	22	.18	4.4	0.025	0.6	7.00	MW	CG	N
0.125	3.18	A12-9	.25	6.4	.107	2.7	1.0	.18	.17	4.3	.17	.76	.08	2.1	0.009	0.2	8.00	MW	C	Z
0.125	3.18	BB-49	.25	6.4	.105	2.7	1.2	.21	.14	3.6	.17	.74	.11	2.8	0.010	0.3	10.0	MW	C	N
0.125	3.18	B1-25	.25	6.4	.095	2.4	12	2.1	.13	3.3	1.6	7.0	.10	2.5	0.015	0.4	6.50	MW	CG	GI
0.125	3.18	B1-8	.25	6.4	.093	2.4	16	2.8	.12	3.0	1.9	8.5	.10	2.6	0.016	0.4	6.50	MW	CG	N
0.125	3.18	FF-43	.25	6.4	.093	2.4	12	2.1	.11	2.8	1.3	5.7	.14	3.5	0.016	0.4	7.50	SST	C	N
0.125	3.18	S-834	.25	6.4	.093	2.4	10	1.8	.10	2.6	1.1	4.8	.15	3.7	0.016	0.4	8.13	SST	C	N
0.125	3.18	B5-53	.25	6.4	.091	2.3	22	3.9	.10	2.6	2.3	10	.12	3.1	0.017	0.4	6.25	MW	C	N
0.125	3.18	2628	.25	6.4	.089	2.3	23	4.1	.10	2.6	2.4	11	.15	3.8	0.018	0.5	7.50	MW	C	Z
0.125	3.18	B1-20	.25	6.4	.089	2.3	21	3.6	.09	2.2	1.8	8.0	.13	3.3	0.018	0.5	7.25	SST	CG	N
0.125	3.18	M-14	.25	6.4	.087	2.2	23	4.0	.09	2.3	2.1	9.3	.15	3.9	0.019	0.5	8.00	SST	CG	N
0.125	3.18	B5-3	.25	6.4	.087	2.2	30	5.2	.11	2.7	3.2	14	.14	3.5	0.019	0.5	7.25	MW	CG	N
0.125	3.18	10814	.25	6.4	.085	2.2	39	6.9	.06	1.6	2.4	11	.15	3.8	0.020	0.5	6.50	SST	C	N
0.125	3.18	J-68	.25	6.4	.085	2.2	31	5.5	.10	2.5	3.1	14	.15	3.9	0.020	0.5	7.00	MW	C	Z
0.125	3.18																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.125	3.18	B1-14	.31	7.9	.091	2.3	16	2.8	.14	3.6	2.3	10	.14	3.5	0.017	0.4	8.00	MW	CG	GI
0.125	3.18	G-66	.31	7.9	.091	2.3	14	2.5	.15	3.7	2.1	9.2	.17	4.2	0.017	0.4	8.75	MW	C	Z
0.125	3.18	U-79	.31	7.9	.091	2.3	11	1.9	.11	2.7	1.1	5.1	.20	5.2	0.017	0.4	11.0	MW	C	N
0.125	3.18	A13-23	.31	7.9	.089	2.3	16	2.8	.11	2.8	1.8	8.0	.18	4.5	0.018	0.5	8.75	SST	C	N
0.125	3.18	L-91	.31	7.9	.083	2.1	41	7.3	.10	2.6	4.2	19	.19	4.8	0.021	0.5	8.00	MW	C	GI
0.125	3.18	L-1	.31	7.9	.081	2.1	49	8.6	.10	2.5	4.8	21	.20	5.2	0.022	0.6	8.25	MW	C	N
0.125	3.18	TT-3	.31	7.9	.081	2.1	45	7.8	.07	1.8	3.2	14	.18	4.5	0.022	0.6	8.00	SST	CG	N
0.125	3.18	NN-60	.31	7.9	.077	2.0	93	16	.07	1.7	6.2	27	.17	4.3	0.024	0.6	7.00	MW	C	N
0.125	3.18	KK-18	.31	7.9	.075	1.9	81	14	.05	1.4	4.4	19	.23	5.7	0.025	0.6	8.00	SST	C	N
0.125	3.18	3196	.34	8.7	.101	2.6	3.9	.68	.23	5.9	.91	4.0	.10	2.5	0.012	0.3	7.33	MW	C	Z
0.125	3.18	FF-86	.34	8.7	.101	2.6	2.8	.48	.22	5.5	.60	2.7	.13	3.2	0.012	0.3	9.50	MW	C	N
0.125	3.18	V-69	.34	8.7	.095	2.4	5.5	.96	.16	4.1	.89	4.0	.18	4.6	0.015	0.4	12.0	MW	CG	N
0.125	3.18	N-16	.34	8.7	.093	2.4	12	2.1	.16	4.0	1.9	8.5	.14	3.7	0.016	0.4	8.00	MW	C	N
0.125	3.18	B6-5	.34	8.7	.085	2.2	22	3.9	.11	2.8	2.4	11	.20	5.1	0.020	0.5	10.0	SST	CG	N
0.125	3.18	G-18	.34	8.7	.083	2.1	45	7.9	.09	2.4	4.2	19	.18	4.5	0.021	0.5	7.50	MW	C	N
0.125	3.18	A13-21	.34	8.7	.079	2.0	50	8.7	.07	1.8	3.6	16	.22	5.7	0.023	0.6	8.75	SST	C	N
0.125	3.18	B-57	.34	8.7	.073	1.9	113	20	.06	1.6	7.3	32	.23	5.9	0.026	0.7	8.00	MW	C	N
0.125	3.18	L-11	.38	9.5	.099	2.5	2.7	.47	.21	5.4	.57	2.5	.16	4.1	0.013	0.3	11.5	SST	C	N
0.125	3.18	II-94	.38	9.5	.095	2.4	6.8	1.2	.15	3.9	1.1	4.7	.15	3.8	0.015	0.4	10.0	SST	C	N
0.125	3.18	U-9	.38	9.5	.095	2.4	6.8	1.2	.23	5.7	1.5	6.8	.15	3.8	0.015	0.4	10.0	MW	CG	N
0.125	3.18	O-15	.38	9.5	.093	2.4	10	1.8	.18	4.7	1.9	8.5	.16	4.1	0.016	0.4	9.00	MW	C	N
0.125	3.18	A11-11	.38	9.5	.091	2.3	11	1.9	.14	3.6	1.5	6.7	.17	4.3	0.017	0.4	10.0	SST	CG	N
0.125	3.18	O-7	.38	9.5	.091	2.3	13	2.2	.18	4.6	2.3	10	.18	4.5	0.017	0.4	9.50	MW	C	N
0.125	3.18	B1-27	.38	9.5	.089	2.3	13	2.3	.14	3.4	1.8	8.0	.18	4.7	0.018	0.5	10.3	SST	CG	N
0.125	3.18	G-15	.38	9.5	.089	2.3	14	2.4	.16	4.0	2.2	9.7	.22	5.5	0.018	0.5	11.0	MW	C	Z
0.125	3.18	H-98	.38	9.5	.085	2.2	22	3.8	.11	2.9	2.4	11	.22	5.6	0.020	0.5	10.0	SST	C	N
0.125	3.18	Q-93	.38	9.5	.085	2.2	17	2.9	.08	1.9	1.2	5.5	.30	7.6	0.020	0.5	14.0	MW	C	GI
0.125	3.18	UU-14	.38	9.5	.085	2.2	33	5.8	.11	2.8	3.7	16	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.125	3.18	DD-69	.38	9.5	.081	2.1	34	6.0	.13	3.4	4.6	20	.24	6.1	0.022	0.6	11.0	MW	CG	N
0.125	3.18	LL-5	.38	9.5	.081	2.1	38	6.7	.08	2.1	3.2	14	.22	5.6	0.022	0.6	9.00	SST	C	N
0.125	3.18	S-700	.38	9.5	.081	2.1	33	5.9	.10	2.4	3.2	14	.24	6.1	0.022	0.6	10.0	SST	C	N
0.125	3.18	A12-7	.38	9.5	.079	2.0	54	9.5	.10	2.6	5.5	24	.23	5.8	0.023	0.6	9.00	MW	C	N
0.125	3.18	10172	.38	9.5	.077	2.0	56	9.8	.11	2.8	6.2	27	.25	6.2	0.024	0.6	10.3	MW	CG	N
0.125	3.18	G-5	.38	9.5	.075	1.9	102	18	.06	1.6	6.5	29	.21	5.4	0.025	0.6	7.50	MW	C	BO
0.125	3.18	NN-85	.38	9.5	.075	1.9	70	12	.06	1.6	4.4	19	.23	5.7	0.025	0.6	9.00	SST	CG	N
0.125	3.18	N-14	.41	10.3	.095	2.4	7.8	1.4	.20	5.1	1.6	7.0	.15	3.8	0.015	0.4	9.00	MW	C	N
0.125	3.18	M-113	.41	10.3	.091	2.3	11	1.9	.20	5.1	2.1	9.5	.20	5.2	0.017	0.4	11.0	MW	C	N
0.125	3.18	B-60	.41	10.3	.089	2.3	14	2.4	.19	4.8	2.6	12	.22	5.5	0.018	0.5	11.0	MW	C	Z
0.125	3.18	B-82	.41	10.3	.089	2.3	14	2.4	.20	5.0	2.7	12	.20	5.0	0.018	0.5	11.0	MW	CG	GI
0.125	3.18	F-74	.41	10.3	.089	2.3	15	2.7	.17	4.4	2.7	12	.20	5.0	0.018	0.5	10.0	MW	C	Z
0.125	3.18	NN-13	.41	10.3	.081	2.1	33	5.9	.10	2.4	3.2	14	.22	5.6	0.022	0.6	10.0	SST	CG	N
0.125	3.18	GG-51	.44	11.1	.095	2.4	4.2	.74	.20	5.0	.83	3.7	.24	6.1	0.015	0.4	15.0	MW	C	GI
0.125	3.18	F-88	.44	11.1	.089	2.3	13	2.2	.21	5.3	2.6	12	.23	5.8	0.018	0.5	11.8	MW	C	Z
0.125	3.18	V-43	.44	11.1	.087	2.2	15	2.7	.14	3.5	2.1	9.3	.23	5.8	0.019	0.5	11.0	SST	C	N
0.125	3.18	S-846	.44	11.1	.081	2.1	27	4.7	.12	3.0	3.2	14	.29	7.3	0.022	0.6	12.0	SST	C	N
0.125	3.18	B12-9	.44	11.1	.079	2.0	37	6.5	.15	3.7	5.5	24	.28	7.2	0.023	0.6	12.3	MW	CG	BO
0.125	3.18	W-79	.44	11.1	.075	1.9	62	11	.07	1.8	4.4	19	.25	6.4	0.025	0.6	10.0	SST	CG	N
0.125	3.18	10832	.47	11.9	.105	2.7	1.3	.22	.36	9.2	.46	2.0	.11	2.7	0.010	0.3	9.50	MW	C	N
0.125	3.18	2765	.47	11.9	.093	2.4	7.7	1.3	.25	6.3	1.9	8.5	.20	5.1	0.016	0.4	11.5	MW	C	Z
0.125	3.18	A10-21	.47	11.9	.083	2.1	23	4.1	.12	3.1	2.8	12	.24	6.1	0.021	0.5	11.5	SST	CG	N
0.125	3.18	A13-12	.47	11.9	.077	2.0	47	8.3	.13	3.3	6.2	27	.31	7.8	0.024	0.6	11.8	MW	C	N
0.125	3.18	11400	.47	11.9	.075	1.9	64	11	.07	1.7	4.4	19	.24	6.2	0.025	0.6	9.75	SST	CG	N
0.125	3.18	DD-3	.50	12.7	.109	2.8	.19	.03	.34	8.6	.06	.28	.16	4.1	0.008	0.2	19.0	SST	C	N
0.125	3.18	B5-67	.50	12.7	.107	2.7	.83	.15	.41	10	.34	1.5	.09	2.3	0.009	0.2	9.25	MW	C	N
0.125	3.18	10068	.50	12.7	.105	2.7	.50	.09	.28	7.1	.14	.62	.22	5.6	0.010	0.3	21.0	MW	C	Z
0.125	3.18	Q-81	.50	12.7	.105	2.7	.33	.06	.18	4.6	.06	.26	.32	8.1	0.010	0.3	31.0	MW	C	N
0.125	3.18	11123	.50	12.7	.105	2.7	1.1	.19	.39	9.8	.43	1.9	.12	2.9	0.010	0.3	10.5	MW	C	N
0.125	3.18	LL-23	.50	12.7	.105	2.7	1.2	.21	.28	7.1	.34	1.5	.10	2.5	0.010	0.3	9.00	SST	C	N
0.125	3.18	B-407	.50	12.7	.101	2.6	2.2	.39	.35	9.0	.79	3.5	.15	3.7	0.012	0.3	11.3	MW	C	Z
0.125	3.18	B-408	.50	12.7	.099	2.5	3.0	.52	.33	8.5	1.0	4.5	.17	4.2	0.013	0.3	11.8	MW	C	Z
0.125	3.18	U-85	.50	12.7	.097	2.5	3.7	.64	.30	7.7	1.1	5.0	.20	5.0	0.014	0.4	13.0	MW	C	N
0.125	3.18	S-202	.50	12.7	.095	2.4	7.3	1.3	.14	3.7	1.1	4.7	.14	3.6	0.015	0.4	8.50	SST	C	N
0.125	3.18	3117	.50	12.7	.093	2.4	7.8	1.4	.25	6.2	1.9	8.5	.20	5.0	0.016	0.4	11.3	MW	C	GI
0.125	3.18	A14-11	.50	12.7	.093	2.4	6.1	1.1	.21	5.3	1.3	5.7	.20	5.1	0.016	0.4	12.5	SST	CG	N
0.125	3.18	B-409	.50	12.7	.093	2.4	7.1	1.2	.27	6.8	1.9	8.5	.21	5.4	0.016	0.4	12.3	MW	C	Z
0.125	3.18	G-90	.50	12.7	.093	2.4	7.3	1.3	.26	6.7	1.9	8.5	.21	5.3	0.016	0.4	12.0	MW	C	N
0.125	3.18	S-320	.50	12.7	.093	2.4	6.7	1.2	.19	4.8	1.3	5.7	.18	4.7	0.016	0.4	11.5	SST	CG	N
0.125	3.18	F-100	.50	12.7	.093	2.4	6.9	1.2	.28	7.0	1.9	8.5	.20	5.1	0.016	0.4	12.5	MW	CG	N
0.125	3.18	A14-21	.50	12.7	.089	2.3	9.5	1.7	.19	4.8	1.8	8.0	.24	6.2	0.018	0.5	13.5	SST	CG	N
0.125	3.18	B-410	.50	12.7	.089	2.3	11	1.9	.24	6.1	2.6	11	.26	6.6	0.018</					




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.125	3.18	A-21	.53	13.5	.085	2.2	18	3.1	.14	3.5	2.4	11	.26	6.6	0.020	0.5	12.0	SST	C	N
0.125	3.18	B10-25	.56	14.3	.097	2.5	3.4	.60	.36	9.0	1.2	5.4	.21	5.2	0.014	0.4	13.8	MW	C	N
0.125	3.18	J-69	.56	14.3	.091	2.3	7.3	1.3	.29	7.4	2.1	9.5	.27	6.9	0.017	0.4	15.0	MW	C	Z
0.125	3.18	L-79	.56	14.3	.083	2.1	15	2.7	.18	4.5	2.7	12	.38	9.7	0.021	0.5	18.3	MW	CG	Z
0.125	3.18	S-1012	.59	15.1	.099	2.5	2.3	.40	.32	8.2	.73	3.2	.19	4.7	0.013	0.3	13.3	SST	C	N
0.125	3.18	S-937	.59	15.1	.089	2.3	7.7	1.4	.23	5.9	1.8	8.0	.30	7.7	0.018	0.5	15.9	SST	C	N
0.125	3.18	G-27	.59	15.1	.063	1.6	133	23	.09	2.2	12	52	.47	11.8	0.031	0.8	14.0	MW	C	N
0.125	3.18	A-1	.63	15.9	.105	2.7	.95	.17	.50	13	.47	2.1	.13	3.3	0.010	0.3	12.0	MW	C	N
0.125	3.18	390	.63	15.9	.103	2.6	1.6	.28	.44	11	.70	3.1	.13	3.4	0.011	0.3	11.0	MW	C	Z
0.125	3.18	A-43	.63	15.9	.103	2.6	1.2	.22	.47	12	.58	2.6	.16	4.1	0.011	0.3	13.5	MW	C	BO
0.125	3.18	N-22	.63	15.9	.103	2.6	1.3	.23	.47	12	.61	2.7	.15	3.9	0.011	0.3	13.0	MW	C	N
0.125	3.18	S-1445	.63	15.9	.099	2.5	1.3	.23	.35	8.8	.45	2.0	.28	7.1	0.013	0.3	21.5	SST	CG	N
0.125	3.18	J-89	.63	15.9	.097	2.5	3.3	.58	.41	10	1.4	6.0	.21	5.4	0.014	0.4	14.3	MW	C	N
0.125	3.18	B14-9	.63	15.9	.097	2.5	3.1	.54	.40	10	1.2	5.5	.22	5.7	0.014	0.4	15.0	MW	C	N
0.125	3.18	EE-61	.63	15.9	.095	2.4	4.2	.74	.38	9.6	1.6	7.0	.24	6.1	0.015	0.4	15.0	MW	C	N
0.125	3.18	S-1543	.63	15.9	.095	2.4	4.4	.77	.24	6.1	1.1	4.7	.21	5.3	0.015	0.4	13.0	SST	C	N
0.125	3.18	A10-20	.63	15.9	.089	2.3	11	2.0	.24	6.0	2.7	12	.25	6.3	0.018	0.5	12.8	MW	C	N
0.125	3.18	F-5	.63	15.9	.089	2.3	8.8	1.5	.31	7.8	2.7	12	.31	7.8	0.018	0.5	16.0	MW	C	Z
0.125	3.18	B1-19	.63	15.9	.079	2.0	25	4.4	.22	5.5	5.5	24	.39	9.9	0.023	0.6	17.0	MW	CG	GI
0.125	3.18	G-2	.63	15.9	.075	1.9	28	4.8	.10	2.5	2.8	12	.53	13.3	0.025	0.6	20.0	SST	C	N
0.125	3.18	2544	.63	15.9	.073	1.9	68	12	.11	2.7	7.3	32	.34	8.6	0.026	0.7	12.0	MW	C	Z
0.125	3.18	903	.63	15.9	.069	1.8	97	17	.09	2.3	8.9	40	.36	9.2	0.028	0.7	12.0	MW	C	Z
0.125	3.18	J-64	.66	16.7	.095	2.4	2.4	.42	.33	8.3	.79	3.5	.33	8.4	0.015	0.4	22.0	SST	CG	N
0.125	3.18	S-11	.66	16.7	.095	2.4	2.4	.41	.30	7.7	.72	3.2	.35	9.0	0.015	0.4	22.5	SST	C	N
0.125	3.18	3546	.66	16.7	.085	2.2	16	2.8	.23	5.8	3.7	16	.31	7.9	0.020	0.5	14.5	MW	C	Z
0.125	3.18	FF-51	.69	17.4	.105	2.7	.35	.06	.39	9.8	.14	.60	.30	7.6	0.010	0.3	29.0	MW	C	N
0.125	3.18	A-80	.69	17.4	.101	2.6	1.4	.25	.41	10	.58	2.6	.19	4.9	0.012	0.3	15.0	SST	C	N
0.125	3.18	A13-22	.69	17.4	.089	2.3	6.8	1.2	.26	6.7	1.8	8.0	.32	8.2	0.018	0.5	18.0	SST	CG	N
0.125	3.18	F-72	.69	17.4	.085	2.2	12	2.2	.29	7.5	3.7	16	.38	9.7	0.020	0.5	18.0	MW	C	Z
0.125	3.18	NN-9	.69	17.4	.079	2.0	22	3.9	.24	6.2	5.5	24	.44	11.1	0.023	0.6	19.0	MW	CG	N
0.125	3.18	J-75	.69	17.4	.075	1.9	26	4.5	.14	3.5	3.5	16	.55	14.0	0.025	0.6	21.0	SST	C	N
0.125	3.18	B4-9	.70	17.9	.095	2.4	4.3	.76	.24	6.2	1.1	4.7	.20	5.0	0.015	0.4	13.0	SST	CG	N
0.125	3.18	B12-7	.72	18.2	.095	2.4	3.7	.65	.43	11	1.6	7.0	.25	6.4	0.015	0.4	16.8	MW	CG	N
0.125	3.18	S-1687	.73	18.6	.095	2.4	4.0	.69	.27	6.7	1.1	4.7	.23	5.7	0.015	0.4	14.0	SST	C	N
0.125	3.18	B4-4	.73	18.6	.089	2.3	7.5	1.3	.36	9.2	2.7	12	.35	8.9	0.018	0.5	18.5	MW	C	N
0.125	3.18	915	.75	19.1	.101	2.6	1.5	.26	.55	14	.81	3.6	.20	5.2	0.012	0.3	16.0	MW	C	Z
0.125	3.18	JJ-27	.75	19.1	.101	2.6	1.6	.28	.56	14	.91	4.0	.19	4.8	0.012	0.3	14.8	MW	C	N
0.125	3.18	A11-15	.75	19.1	.093	2.4	3.9	.68	.32	8.3	1.3	5.7	.30	7.5	0.016	0.4	18.5	SST	CG	N
0.125	3.18	F-3	.75	19.1	.089	2.3	7.0	1.2	.38	9.7	2.7	12	.37	9.4	0.018	0.5	19.5	MW	C	Z
0.125	3.18	A13-50	.75	19.1	.087	2.2	8.9	1.6	.36	9.0	3.2	14	.38	9.5	0.019	0.5	19.8	MW	CG	GI
0.125	3.18	00-21	.75	19.1	.085	2.2	11	1.9	.33	8.4	3.6	16	.42	10.7	0.020	0.5	20.0	MW	C	N
0.125	3.18	KK-31	.75	19.1	.085	2.2	12	2.0	.31	7.9	3.7	16	.40	10.2	0.020	0.5	19.0	MW	C	N
0.125	3.18	S-702	.75	19.1	.081	2.1	15	2.6	.21	5.4	3.2	14	.46	11.7	0.022	0.6	20.0	SST	C	N
0.125	3.18	B14-18	.75	19.1	.081	2.1	20	3.5	.24	6.1	4.8	21	.44	11.2	0.022	0.6	20.0	MW	CG	N
0.125	3.18	A10-24	.75	19.1	.079	2.0	20	3.5	.18	4.7	3.6	16	.46	11.7	0.023	0.6	19.0	SST	C	N
0.125	3.18	10957	.78	19.8	.101	2.6	1.3	.22	.55	14	.68	3.0	.23	5.9	0.012	0.3	18.5	MW	C	Z
0.125	3.18	TT-9	.78	19.8	.089	2.3	5.6	.98	.32	8.1	1.8	8.0	.41	10.3	0.018	0.5	21.5	SST	C	N
0.125	3.18	B5-54	.78	19.8	.079	2.0	19	3.3	.28	7.0	5.2	23	.51	12.9	0.023	0.6	22.0	MW	CG	GI
0.125	3.18	AA-70	.81	20.6	.109	2.8	.30	.05	.57	14	.17	.77	.11	2.7	0.008	0.2	12.5	SST	C	N
0.125	3.18	1719	.81	20.6	.105	2.7	.84	.15	.63	16	.53	2.4	.14	3.6	0.010	0.3	13.3	MW	C	Z
0.125	3.18	S-881	.81	20.6	.099	2.5	1.3	.23	.52	13	.68	3.0	.29	7.4	0.013	0.3	21.5	SST	C	N
0.125	3.18	B4-3	.81	20.6	.095	2.4	5.0	.87	.32	8.1	1.6	7.0	.21	5.3	0.015	0.4	13.0	MW	C	N
0.125	3.18	S-792	.84	21.4	.101	2.6	1.0	.18	.57	14	.58	2.6	.25	6.4	0.012	0.3	20.0	SST	C	N
0.125	3.18	10943	.84	21.4	.091	2.3	8.3	1.5	.28	7.0	2.3	10	.25	6.3	0.017	0.4	13.5	MW	C	Z
0.125	3.18	KK-41	.84	21.4	.081	2.1	20	3.5	.16	4.1	3.2	14	.36	9.2	0.022	0.6	15.5	SST	C	N
0.125	3.18	00-69	.88	22.2	.105	2.7	.30	.05	.53	13	.16	.70	.35	8.8	0.010	0.3	33.8	MW	C	N
0.125	3.18	S-1511	.88	22.2	.095	2.4	4.0	.69	.27	6.7	1.1	4.7	.23	5.7	0.015	0.4	14.0	SST	C	N
0.125	3.18	B7-15	.91	23.0	.091	2.3	5.4	.95	.42	11	2.3	10	.35	8.9	0.017	0.4	19.5	MW	C	N
0.125	3.18	KK-82	.91	23.0	.085	2.2	10	1.8	.35	8.9	3.7	16	.44	11.2	0.020	0.5	21.0	MW	C	N
0.125	3.18	Y-85	.91	23.0	.085	2.2	9.7	1.7	.38	9.6	3.7	16	.47	11.9	0.020	0.5	22.5	MW	C	GI
0.125	3.18	LL-89	.94	23.8	.085	2.2	8.6	1.5	.42	11	3.6	16	.52	13.2	0.020	0.5	25.0	MW	C	N
0.125	3.18	MM-66	.94	23.8	.065	1.7	55	9.6	.13	3.3	7.2	32	.71	17.9	0.030	0.8	23.5	SST	CG	N
0.125	3.18	10745	1.00	25.4	.107	2.7	.42	.07	.85	21	.36	1.6	.16	3.9	0.009	0.2	16.3	MW	C	N
0.125	3.18	391	1.00	25.4	.103	2.6	.96	.17	.73	18	.70	3.1	.20	5.0	0.011	0.3	16.8	MW	C	Z
0.125	3.18	354-A	1.00	25.4	.097	2.5	2.2	.39	.64	16	1.4	6.3	.30	7.6	0.014	0.4	20.3	MW	C	Z
0.125	3.18	G-7	1.00	25.4	.097	2.5	1.9	.33	.66	17	1.2	5.5	.34	8.7	0.014	0.4	23.5	MW	C	BO
0.125	3.18	II-59	1.00	25.4	.095	2.4	3.0	.53	.52	13	1.6	7.0	.32	8.0	0.015	0.4	20.0	MW	C	Z
0.125	3.18	M-143	1.00	25.4	.095	2.4	2.1	.37	.57	14	1.2	5.3	.44	11.0	0.015	0.4	28.0	MW	C	Z
0.125	3.18	00-15	1.00	25.4	.095	2.4	3.4	.60	.46	12	1.6	7.0	.29	7.2	0.015	0.4	18.0	MW	C	N



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.125	3.18	B15-63	1.22	31.0	.099	2.5	1.0	.18	.80	20	.81	3.6	.42	10.6	0.013	0.3	31.0	MW	C	N
0.125	3.18	S-1085	1.25	31.8	.095	2.4	2.4	.43	.43	11	1.1	4.7	.34	8.6	0.015	0.4	21.5	SST	C	N
0.125	3.18	PP-9	1.25	31.8	.065	1.7	100	18	.07	1.8	7.2	32	.45	11.4	0.030	0.8	14.0	SST	C	N
0.125	3.18	AA-7	1.38	34.9	.105	2.7	.47	.08	.72	18	.34	1.5	.21	5.3	0.010	0.3	20.0	SST	C	N
0.125	3.18	354-B	1.38	34.9	.097	2.5	1.6	.28	.90	23	1.4	6.3	.40	10.1	0.014	0.4	27.5	MW	C	Z
0.125	3.18	1827	1.38	34.9	.093	2.4	2.3	.41	.81	21	1.9	8.5	.54	13.8	0.016	0.4	33.0	MW	C	Z
0.125	3.18	KK-90	1.38	34.9	.089	2.3	4.9	.86	.55	14	2.7	12	.50	12.8	0.018	0.5	27.0	MW	C	N
0.125	3.18	MM-82	1.38	34.9	.087	2.2	6.6	1.1	.48	12	3.2	14	.51	13.0	0.019	0.5	26.0	MW	C	Z
0.125	3.18	FF-54	1.38	34.9	.085	2.2	7.9	1.4	.46	12	3.7	16	.56	14.2	0.020	0.5	27.0	MW	C	N
0.125	3.18	NN-94	1.50	38.1	.075	1.9	13	2.3	.33	8.4	4.4	19	1.00	25.4	0.025	0.6	39.0	SST	C	N
0.125	3.18	2982	1.53	38.9	.095	2.4	3.1	.55	.51	13	1.6	7.0	.31	7.8	0.015	0.4	19.5	MW	C	Z
0.125	3.18	354-C	1.75	44.5	.097	2.5	1.2	.22	1.1	29	1.4	6.3	.50	12.6	0.014	0.4	34.5	MW	C	Z
0.125	3.18	BB-34	2.25	57.2	.085	2.2	5.7	.99	.64	16	3.7	16	.76	19.3	0.020	0.5	37.0	MW	C	N
0.125	3.18	Y-65	3.00	76.2	.105	2.7	.21	.04	2.5	64	.52	2.3	.49	12.4	0.010	0.3	48.0	MW	C	N
0.125	3.18	S-1474	4.25	108.0	.105	2.7	.08	.01	3.2	82	.27	1.2	1.02	25.9	0.010	0.3	101.0	SST	C	N
0.140	3.56	10224	.16	4.0	.122	3.1	1.2	.21	.10	2.5	.12	.52	.06	1.5	0.009	0.2	5.50	MW	C	N
0.140	3.56	DD-49	.19	4.8	.116	2.9	4.2	.74	.12	2.9	.49	2.2	.07	1.8	0.012	0.3	5.00	SST	C	N
0.140	3.56	J-84	.20	5.2	.100	2.5	67	12	.05	1.3	3.3	15	.08	2.0	0.020	0.5	4.00	MW	CG	N
0.140	3.56	U-93	.25	6.4	.118	3.0	1.6	.29	.15	3.8	.25	1.1	.10	2.5	0.011	0.3	8.00	MW	C	Z
0.140	3.56	Z-7	.25	6.4	.112	2.8	3.8	.67	.12	3.1	.46	2.1	.13	3.3	0.014	0.4	8.25	SST	C	N
0.140	3.56	II-9	.25	6.4	.096	2.4	102	18	.04	1.1	4.4	19	.11	2.8	0.022	0.6	4.00	MW	C	N
0.140	3.56	JJ-72	.25	6.4	.080	2.0	155	27	.04	1.1	6.6	30	.18	4.6	0.030	0.8	5.00	SST	O	N
0.140	3.56	OO-19	.28	7.1	.120	3.0	1.0	.18	.19	4.7	.19	.83	.10	2.4	0.010	0.3	8.50	MW	C	N
0.140	3.56	L-97	.28	7.1	.116	2.9	2.0	.36	.16	4.1	.33	1.5	.12	3.0	0.012	0.3	9.00	MW	C	N
0.140	3.56	GG-60	.31	7.9	.112	2.8	2.7	.47	.16	4.0	.42	1.9	.15	3.9	0.014	0.4	11.0	SST	CG	N
0.140	3.56	B8-8	.31	7.9	.104	2.6	14	2.4	.15	3.8	2.1	9.2	.16	4.1	0.018	0.5	8.00	MW	C	N
0.140	3.56	AA-6	.31	7.9	.100	2.5	27	4.7	.12	3.2	3.3	15	.14	3.6	0.020	0.5	7.00	MW	CG	Z
0.140	3.56	LL-69	.31	7.9	.090	2.3	49	8.6	.08	2.0	4.0	18	.21	5.4	0.025	0.6	8.50	SST	CG	N
0.140	3.56	A9-27	.34	8.7	.098	2.5	27	4.7	.09	2.4	2.5	11	.18	4.5	0.021	0.5	7.50	SST	C	N
0.140	3.56	CC-91	.34	8.7	.088	2.2	57	10	.08	2.0	4.4	20	.23	5.8	0.026	0.7	8.75	SST	CG	N
0.140	3.56	NN-41	.34	8.7	.088	2.2	66	11	.07	1.7	4.4	20	.21	5.3	0.026	0.7	8.00	SST	CG	N
0.140	3.56	H-77	.34	8.7	.084	2.1	78	14	.07	1.8	5.5	24	.25	6.4	0.028	0.7	9.00	SST	CG	N
0.140	3.56	A-27	.34	8.7	.082	2.1	110	19	.05	1.4	6.0	27	.26	6.6	0.029	0.7	8.00	SST	C	N
0.140	3.56	A12-1	.35	8.9	.112	2.8	4.0	.70	.20	5.2	.82	3.6	.13	3.2	0.014	0.4	8.00	SST	C	N
0.140	3.56	O-80	.36	9.1	.100	2.5	41	7.2	.05	1.4	2.2	9.8	.12	3.0	0.020	0.5	4.88	SST	C	N
0.140	3.56	J-26	.38	9.5	.116	2.9	2.8	.50	.28	7.1	.79	3.5	.10	2.4	0.012	0.3	7.00	MW	C	GI
0.140	3.56	12619	.38	9.5	.116	2.9	2.6	.45	.27	6.9	.71	3.1	.10	2.6	0.012	0.3	7.50	MW	C	N
0.140	3.56	B2-23	.38	9.5	.116	2.9	2.2	.38	.26	6.6	.57	2.5	.11	2.9	0.012	0.3	8.50	MW	C	Z
0.140	3.56	A15-25	.38	9.5	.114	2.9	4.0	.70	.26	6.5	1.0	4.6	.10	2.5	0.013	0.3	7.00	MW	C	GI
0.140	3.56	FF-22	.38	9.5	.114	2.9	4.0	.70	.20	5.1	.80	3.6	.10	2.6	0.013	0.3	7.00	BC	C	N
0.140	3.56	M-129	.38	9.5	.110	2.8	5.7	1.0	.23	5.9	1.3	5.9	.14	3.6	0.015	0.4	8.50	MW	C	N
0.140	3.56	A15-6	.38	9.5	.100	2.5	21	3.6	.11	2.7	2.2	9.8	.18	4.4	0.020	0.5	7.75	SST	C	N
0.140	3.56	AA-42	.38	9.5	.100	2.5	13	2.3	.16	3.9	2.0	8.9	.22	5.6	0.020	0.5	11.0	SST	CG	N
0.140	3.56	GG-38	.38	9.5	.100	2.5	18	3.1	.12	3.1	2.2	9.8	.19	4.8	0.020	0.5	8.50	SST	C	N
0.140	3.56	3762	.38	9.5	.084	2.1	157	28	.05	1.3	8.2	36	.20	5.0	0.028	0.7	6.00	MW	C	Z
0.140	3.56	H-95	.38	9.5	.084	2.1	126	22	.06	1.6	8.2	36	.22	5.7	0.028	0.7	7.00	MW	C	N
0.140	3.56	S-1535	.39	9.9	.078	2.0	162	28.3	.045	1.14	7.3	32.5	.23	5.9	0.031	0.8	7.50	SST	CG	N
0.140	3.56	11375	.41	10.3	.108	2.7	7.0	1.2	.16	4.1	1.1	5.1	.15	3.8	0.016	0.4	8.25	SST	C	N
0.140	3.56	3633	.41	10.3	.104	2.6	14	2.4	.18	4.5	2.4	11	.14	3.7	0.018	0.5	8.00	MW	CG	N
0.140	3.56	J-80	.41	10.3	.102	2.6	14	2.4	.14	3.5	1.9	8.4	.17	4.2	0.019	0.5	8.75	SST	CG	N
0.140	3.56	UU-4	.42	10.7	.100	2.5	17	3.0	.13	3.3	2.2	9.8	.20	5.1	0.020	0.5	9.00	SST	C	N
0.140	3.56	B1-10	.44	11.1	.124	3.1	.26	.05	.34	8.7	.09	.40	.09	2.4	0.008	0.2	10.8	SST	C	N
0.140	3.56	J-99	.44	11.1	.116	2.9	1.1	.19	.25	6.2	.27	1.2	.19	4.9	0.012	0.3	15.0	MW	C	Z
0.140	3.56	3793	.44	11.1	.108	2.7	7.9	1.4	.22	5.5	1.7	7.7	.15	3.8	0.016	0.4	8.25	MW	C	Z
0.140	3.56	V-40	.44	11.1	.106	2.7	6.5	1.1	.22	5.5	1.4	6.2	.22	5.6	0.017	0.4	12.0	MW	C	N
0.140	3.56	B14-56	.44	11.1	.104	2.6	17	2.9	.15	3.7	2.4	11	.14	3.7	0.018	0.5	7.00	MW	C	N
0.140	3.56	J-90	.44	11.1	.102	2.6	13	2.3	.22	5.5	2.8	13	.21	5.3	0.019	0.5	10.0	MW	C	Z
0.140	3.56	V-41	.44	11.1	.102	2.6	11	1.9	.19	4.9	2.0	9.0	.25	6.3	0.019	0.5	12.0	MW	C	N
0.140	3.56	OO-22	.45	11.5	.100	2.5	27	4.7	.12	3.2	3.3	15								



1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.140	3.56	Q-83	.72	18.2	.092	2.3	21	3.7	.27	6.7	5.6	25	.42	10.7	0.024	0.6	16.5	MW	C	N
0.140	3.56	10968	.75	19.1	.120	3.0	.50	.09	.59	15	.30	1.3	.16	4.1	0.010	0.3	15.0	MW	C	Z
0.140	3.56	RR-35	.75	19.1	.100	2.5	4.5	.79	.18	4.6	.82	3.6	.57	14.5	0.020	0.5	27.5	SST	C	N
0.140	3.56	JJ-25	.78	19.8	.088	2.2	21	3.8	.21	5.3	4.4	20	.52	13.2	0.026	0.7	20.0	SST	CG	N
0.140	3.56	11464	.81	20.6	.114	2.9	2.2	.39	.30	7.5	.66	2.9	.14	3.6	0.013	0.3	10.0	SST	C	N
0.140	3.56	RR-44	.81	20.6	.100	2.5	6.4	1.1	.34	8.7	2.2	9.8	.42	10.7	0.020	0.5	20.0	SST	C	N
0.140	3.56	FF-53	.88	22.2	.120	3.0	.47	.08	.71	18	.33	1.5	.17	4.3	0.010	0.3	16.0	MW	C	N
0.140	3.56	3195	.88	22.2	.116	2.9	1.0	.18	.67	17	.68	3.0	.20	5.2	0.012	0.3	16.0	MW	C	Z
0.140	3.56	1831	.91	23.0	.116	2.9	1.1	.19	.71	18	.78	3.5	.19	4.9	0.012	0.3	15.0	MW	C	Z
0.140	3.56	3707	.94	23.8	.120	3.0	.33	.06	.71	18	.23	1.0	.23	5.8	0.010	0.3	22.0	MW	C	Z
0.140	3.56	B5-69	.94	23.8	.118	3.0	.34	.06	.59	15	.20	.88	.35	8.9	0.011	0.3	31.0	MW	C	N
0.140	3.56	S-393	.94	23.8	.108	2.7	2.2	.39	.51	13	1.1	5.1	.36	9.1	0.016	0.4	21.5	SST	C	N
0.140	3.56	A10-34	1.00	25.4	.116	2.9	.61	.11	.72	18	.43	1.9	.29	7.2	0.012	0.3	22.8	SST	C	N
0.140	3.56	3773	1.00	25.4	.108	2.7	3.5	.62	.49	12	1.7	7.7	.27	6.9	0.016	0.4	16.0	MW	C	Z
0.140	3.56	11254	1.00	25.4	.102	2.6	4.7	.82	.40	10	1.9	8.4	.44	11.1	0.019	0.5	22.0	SST	C	N
0.140	3.56	NN-55	1.03	26.2	.108	2.7	3.3	.58	.52	13	1.7	7.7	.29	7.3	0.016	0.4	17.0	MW	C	N
0.140	3.56	BB-83	1.06	27.0	.096	2.4	7.1	1.2	.41	10	2.9	13	.62	15.6	0.022	0.6	27.0	SST	C	N
0.140	3.56	LL-19	1.13	28.6	.120	3.0	.26	.05	.85	21	.22	.98	.28	7.1	0.010	0.3	27.0	MW	C	N
0.140	3.56	PP-54	1.13	28.6	.108	2.7	1.8	.31	.63	16	1.1	4.9	.50	12.6	0.016	0.4	30.0	MW	C	Z
0.140	3.56	LL-91	1.25	31.8	.124	3.1	.14	.02	1.1	27	.15	.68	.17	4.3	0.008	0.2	20.0	MW	C	N
0.140	3.56	4223	1.25	31.8	.110	2.8	1.3	.22	.76	19	.96	4.3	.49	12.4	0.015	0.4	31.5	MW	C	Z
0.140	3.56	S-1020	1.31	33.3	.100	2.5	4.0	.70	.55	14	2.2	9.8	.64	16.3	0.020	0.5	31.0	SST	C	N
0.140	3.56	B3-41	1.31	33.3	.080	2.0	30	5.3	.33	8.3	9.9	44	.93	23.6	0.030	0.8	31.0	MW	CG	N
0.140	3.56	AA-68	1.34	34.1	.104	2.6	4.9	.86	.33	8.3	1.6	7.2	.32	8.2	0.018	0.5	17.0	SST	C	N
0.140	3.56	1755	1.38	34.9	.108	2.7	1.6	.28	.84	21	1.4	6.0	.54	13.6	0.016	0.4	32.5	MW	C	Z
0.140	3.56	2638	1.38	34.9	.102	2.6	3.6	.62	.75	19	2.7	12	.62	15.8	0.019	0.5	31.8	MW	C	Z
0.140	3.56	N-108	1.44	36.5	.092	2.3	10	1.8	.55	14	5.6	25	.79	20.1	0.024	0.6	32.0	MW	C	GI
0.140	3.56	A12-34	1.44	36.6	.116	2.9	.43	.07	1.1	27	.45	2.0	.38	9.8	0.012	0.3	31.0	SST	C	N
0.140	3.56	1922	1.50	38.1	.108	2.7	1.7	.30	.98	25	1.7	7.4	.52	13.1	0.016	0.4	31.3	MW	C	Z
0.140	3.56	O-128	1.94	49.2	.090	2.3	7.1	1.2	.56	14	4.0	18	1.20	30.5	0.025	0.6	47.0	SST	C	N
0.148	3.76	70206	.25	6.4	.106	2.7	34	6.0	.11	2.7	3.6	16	.13	3.2	0.021	0.5	6.00	MW	CG	N
0.148	3.76	70206S	.25	6.4	.106	2.7	30	5.2	.08	2.1	2.4	11	.13	3.2	0.021	0.5	6.00	SST	CG	N
0.148	3.76	70225	.25	6.4	.102	2.6	50	8.7	.09	2.4	4.7	21	.14	3.6	0.023	0.6	6.13	MW	CG	N
0.148	3.76	70225S	.25	6.4	.102	2.6	43	7.6	.07	1.8	3.1	14	.14	3.6	0.023	0.6	6.13	SST	CG	N
0.148	3.76	70207	.31	7.9	.106	2.7	27	4.7	.14	3.5	3.6	16	.15	3.8	0.021	0.5	7.13	MW	CG	N
0.148	3.76	70207S	.31	7.9	.106	2.7	23	4.1	.10	2.6	2.4	11	.15	3.8	0.021	0.5	7.13	SST	CG	N
0.148	3.76	70226	.31	7.9	.102	2.6	38	6.7	.12	3.1	4.7	21	.17	4.3	0.023	0.6	7.38	MW	CG	N
0.148	3.76	70226S	.31	7.9	.102	2.6	33	5.8	.09	2.4	3.1	14	.17	4.3	0.023	0.6	7.38	SST	CG	N
0.148	3.76	70208	.38	9.7	.106	2.7	21	3.7	.17	4.4	3.6	16	.18	4.5	0.021	0.5	8.50	MW	CG	N
0.148	3.76	70208S	.38	9.7	.106	2.7	18	3.2	.13	3.3	2.4	11	.18	4.5	0.021	0.5	8.50	SST	CG	N
0.148	3.76	70227	.38	9.7	.102	2.6	31	5.3	.15	3.9	4.7	21	.20	5.1	0.023	0.6	8.75	MW	CG	N
0.148	3.76	70227S	.38	9.7	.102	2.6	27	4.6	.12	3.0	3.1	14	.20	5.1	0.023	0.6	8.75	SST	CG	N
0.148	3.76	70209	.44	11.2	.106	2.7	18	3.1	.20	5.1	3.6	16	.20	5.1	0.021	0.5	9.63	MW	CG	N
0.148	3.76	70209S	.44	11.2	.106	2.7	16	2.7	.15	3.9	2.4	11	.20	5.1	0.021	0.5	9.63	SST	CG	N
0.148	3.76	70228	.44	11.2	.102	2.6	26	4.6	.18	4.6	4.7	21	.23	5.8	0.023	0.6	9.88	MW	CG	N
0.148	3.76	70228S	.44	11.2	.102	2.6	23	4.0	.14	3.5	3.1	14	.23	5.8	0.023	0.6	9.88	SST	CG	N
0.148	3.76	70210	.50	12.7	.106	2.7	15	2.7	.24	6.0	3.6	16	.23	5.8	0.021	0.5	10.9	MW	CG	N
0.148	3.76	70210S	.50	12.7	.106	2.7	13	2.3	.18	4.6	2.4	11	.23	5.8	0.021	0.5	10.9	SST	CG	N
0.148	3.76	70229	.50	12.7	.102	2.6	23	4.0	.21	5.3	4.7	21	.26	6.5	0.023	0.6	11.1	MW	CG	N
0.148	3.76	70229S	.50	12.7	.102	2.6	20	3.4	.16	4.1	3.1	14	.26	6.5	0.023	0.6	11.1	SST	CG	N
0.148	3.76	70211	.56	14.2	.106	2.7	14	2.4	.27	6.7	3.6	16	.25	6.4	0.021	0.5	12.0	MW	CG	N
0.148	3.76	70211S	.56	14.2	.106	2.7	12	2.1	.20	5.1	2.4	11	.25	6.4	0.021	0.5	12.0	SST	CG	N
0.148	3.76	70230	.56	14.2	.102	2.6	20	3.5	.24	6.0	4.7	21	.29	7.2	0.023	0.6	12.4	MW	CG	N
0.148	3.76	70230S	.56	14.2	.102	2.6	17	3.0	.18	4.6	3.1	14	.29	7.2	0.023	0.6	12.4	SST	CG	N
0.148	3.76	70212	.63	16.0	.106	2.7	12	2.1	.29	7.5	3.6	16	.28	7.0	0.021	0.5	13.1	MW	CG	N
0.148	3.76	70212S	.63	16.0	.106	2.7	11	1.9	.23	5.7	2.4	11	.28	7.0	0.021	0.5	13.1	SST	CG	N
0.148	3.76	70231	.63	16.0	.102	2.6	18	3.1	.27	6.7	4.7	21	.31	8.0	0.023	0.6	13.6	MW	CG	N
0.148	3.76	70231S	.63	16.0	.102	2.6	15	2.7	.20	5.2	3.1	14	.31	8.0	0.023	0.6	13.6	SST	CG	N
0.148	3.76	70213	.69	17.5	.106	2.7	11	1.9	.33	8.3	3.6	16	.30							



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.148	3.76	70237	1.00	25.4	.102	2.6	11	1.9	.44	11	4.7	21	.49	12.4	0.023	0.6	21.3	MW	CG	N
0.148	3.76	70237S	1.00	25.4	.102	2.6	9.3	1.6	.34	8.5	3.1	14	.49	12.4	0.023	0.6	21.3	SST	CG	N
0.148	3.76	70220	1.13	28.7	.106	2.7	6.8	1.2	.53	14	3.6	16	.47	11.8	0.021	0.5	22.1	MW	CG	N
0.148	3.76	70220S	1.13	28.7	.106	2.7	5.9	1.0	.41	10	2.4	11	.47	11.8	0.021	0.5	22.1	SST	CG	N
0.148	3.76	70239	1.13	28.7	.102	2.6	9.8	1.7	.48	12	4.7	21	.53	13.4	0.023	0.6	23.0	MW	CG	N
0.148	3.76	70239S	1.13	28.7	.102	2.6	8.5	1.5	.37	9.3	3.1	14	.53	13.4	0.023	0.6	23.0	SST	CG	N
0.148	3.76	70221	1.25	31.8	.106	2.7	5.9	1.0	.61	15	3.6	16	.53	13.3	0.021	0.5	25.0	MW	CG	N
0.148	3.76	70221S	1.25	31.8	.106	2.7	5.2	.90	.47	12	2.4	11	.53	13.3	0.021	0.5	25.0	SST	CG	N
0.148	3.76	70240	1.25	31.8	.102	2.6	8.5	1.5	.55	14	4.7	21	.60	15.3	0.023	0.6	26.1	MW	CG	N
0.148	3.76	70240S	1.25	31.8	.102	2.6	7.4	1.3	.42	11	3.1	14	.60	15.3	0.023	0.6	26.1	SST	CG	N
0.148	3.76	70223	1.38	35.1	.106	2.7	5.6	.98	.65	16	3.6	16	.55	14.1	0.021	0.5	26.4	MW	CG	N
0.148	3.76	70223S	1.38	35.1	.106	2.7	4.9	.85	.49	13	2.4	11	.55	14.1	0.021	0.5	26.4	SST	CG	N
0.148	3.76	70242	1.38	35.1	.102	2.6	8.0	1.4	.59	15	4.7	21	.64	16.2	0.023	0.6	27.8	MW	CG	N
0.148	3.76	70242S	1.38	35.1	.102	2.6	7.0	1.2	.45	11	3.1	14	.64	16.2	0.023	0.6	27.8	SST	CG	N
0.148	3.76	70224	1.50	38.1	.106	2.7	4.9	.87	.73	19	3.6	16	.62	15.8	0.021	0.5	29.6	MW	CG	N
0.148	3.76	70224S	1.50	38.1	.106	2.7	4.3	.75	.56	14	2.4	11	.62	15.8	0.021	0.5	29.6	SST	CG	N
0.148	3.76	70243	1.50	38.1	.102	2.6	7.1	1.2	.66	17	4.7	21	.71	18.1	0.023	0.6	31.0	MW	CG	N
0.148	3.76	70243S	1.50	38.1	.102	2.6	6.2	1.1	.51	13	3.1	14	.71	18.1	0.023	0.6	31.0	SST	CG	N
0.156	3.96	HH-70	.19	4.8	.116	2.9	46	8.0	.07	1.7	3.0	13	.10	2.5	0.020	0.5	4.00	MW	C	N
0.156	3.96	HH-57	.25	6.4	.132	3.4	2.5	.43	.17	4.4	.43	1.9	.08	2.0	0.012	0.3	5.50	SST	C	N
0.156	3.96	V-18	.25	6.4	.126	3.2	7.5	1.3	.11	2.9	.85	3.8	.09	2.3	0.015	0.4	5.00	SST	C	N
0.156	3.96	904	.25	6.4	.116	2.9	30	5.3	.10	2.5	3.0	13	.12	3.0	0.020	0.5	5.00	MW	C	Z
0.156	3.96	J-86	.25	6.4	.106	2.7	83	15	.06	1.6	5.4	24	.13	3.2	0.025	0.6	5.00	MW	CG	Z
0.156	3.96	KK-7	.28	7.1	.136	3.5	1.3	.23	.20	5.2	.27	1.2	.06	1.5	0.010	0.3	5.00	SST	C	N
0.156	3.96	H-18	.28	7.1	.106	2.7	62	11	.09	2.2	5.4	24	.15	3.8	0.025	0.6	6.00	MW	CG	Z
0.156	3.96	B-46	.28	7.1	.104	2.6	88	15	.05	1.2	4.0	18	.16	4.0	0.026	0.7	5.00	SST	C	N
0.156	3.96	3721	.31	7.9	.142	3.6	.09	.01	.21	5.2	.02	.08	.11	2.7	0.007	0.2	14.3	MW	C	N
0.156	3.96	FF-37	.31	7.9	.126	3.2	3.7	.65	.16	4.1	.60	2.7	.15	3.8	0.015	0.4	9.00	MW	C	Z
0.156	3.96	U-16	.31	7.9	.126	3.2	5.2	.91	.19	4.9	1.0	4.4	.12	3.0	0.015	0.4	7.00	MW	C	Z
0.156	3.96	EE-95	.31	7.9	.124	3.1	8.6	1.5	.18	4.6	1.6	6.9	.11	2.8	0.016	0.4	6.00	MW	C	N
0.156	3.96	S-1038	.31	7.9	.120	3.0	17	2.9	.09	2.2	1.5	6.5	.11	2.7	0.018	0.5	5.00	SST	C	N
0.156	3.96	B8-6	.31	7.9	.118	3.0	12	2.1	.16	4.1	1.9	8.6	.15	3.9	0.019	0.5	8.00	MW	CG	N
0.156	3.96	J-82	.31	7.9	.114	2.9	17	2.9	.12	3.1	2.1	9.2	.19	4.8	0.021	0.5	8.00	SST	C	N
0.156	3.96	Q-11	.31	7.9	.106	2.7	62	11	.09	2.2	5.4	24	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.156	3.96	U-90	.31	7.9	.090	2.3	153	27	.05	1.2	7.3	33	.26	6.7	0.033	0.8	8.00	MW	CG	Z
0.156	3.96	N-5	.34	8.7	.140	3.6	.15	.03	.24	6.0	.04	.16	.11	2.7	0.008	0.2	12.5	SST	C	N
0.156	3.96	S-301	.34	8.7	.140	3.6	.14	.03	.23	5.9	.03	.15	.11	2.8	0.008	0.2	13.0	SST	C	N
0.156	3.96	LL-38	.34	8.7	.118	3.0	13	2.2	.14	3.4	1.7	7.6	.15	3.9	0.019	0.5	7.00	SST	C	N
0.156	3.96	Y-67	.34	8.7	.118	3.0	12	2.1	.17	4.4	2.1	9.3	.17	4.3	0.019	0.5	8.00	MW	C	N
0.156	3.96	2815	.34	8.7	.086	2.2	244	43	.05	1.4	13	59	.25	6.2	0.035	0.9	7.00	MW	CG	Z
0.156	3.96	B4-6	.34	8.7	.114	2.9	21	3.6	.17	4.2	3.4	15	.18	4.5	0.021	0.5	7.50	MW	C	N
0.156	3.96	S-1095	.38	9.5	.126	3.2	2.1	.36	.17	4.2	.34	1.5	.21	5.3	0.015	0.4	13.0	SST	C	N
0.156	3.96	10111	.38	9.5	.124	3.1	7.6	1.3	.20	5.2	1.6	6.9	.12	3.0	0.016	0.4	6.50	MW	C	Z
0.156	3.96	N-28	.38	9.5	.120	3.0	7.2	1.3	.20	5.0	1.4	6.2	.18	4.6	0.018	0.5	10.0	MW	CG	Z
0.156	3.96	O-37	.38	9.5	.116	2.9	18	3.2	.16	4.2	3.0	13	.16	4.1	0.020	0.5	7.00	MW	C	N
0.156	3.96	EE-1	.38	9.5	.116	2.9	9.4	1.6	.15	3.7	1.4	6.0	.23	5.8	0.020	0.5	10.5	SST	C	N
0.156	3.96	BB-73	.38	9.5	.116	2.9	7.1	1.2	.11	2.7	.74	3.3	.27	6.9	0.020	0.5	13.5	SST	CG	N
0.156	3.96	O-104	.38	9.5	.114	2.9	23	4.0	.15	3.9	3.4	15	.17	4.3	0.021	0.5	7.00	MW	C	N
0.156	3.96	B12-34	.38	9.5	.112	2.8	22	3.8	.18	4.7	3.9	18	.19	4.7	0.022	0.6	8.50	MW	CG	GI
0.156	3.96	B3-37	.38	9.5	.110	2.8	31	5.4	.14	3.7	4.5	20	.17	4.4	0.023	0.6	7.50	MW	CG	N
0.156	3.96	H-97	.38	9.5	.106	2.7	45	8.0	.12	3.0	5.4	24	.19	4.8	0.025	0.6	7.50	MW	CG	GI
0.156	3.96	MM-25	.38	9.5	.102	2.6	59	10	.11	2.9	6.7	30	.22	5.5	0.027	0.7	8.00	MW	CG	N
0.156	3.96	G-31	.38	9.5	.100	2.5	94	16	.08	2.0	7.5	33	.21	5.3	0.028	0.7	6.50	MW	C	N
0.156	3.96	W-76	.38	9.5	.096	2.4	84	15	.07	1.8	6.1	27	.27	6.9	0.030	0.8	8.00	SST	C	N
0.156	3.96	B12-29	.38	9.5	.080	2.0	365	64	.03	.84	12	54	.27	6.8	0.038	1.0	7.00	SPR	CG	N
0.156	3.96	B17-135	.41	10.3	.140	3.6	.23	.04	.32	8.1	.07	.32	.09	2.2	0.008	0.2	10.0	MW	C	N
0.156	3.96	M-72	.41	10.3	.138	3.5	.30	.05	.29	7.3	.09	.38	.12	3.0	0.009	0.2	12.0	MW	C	N
0.156	3.96	B15-11	.41	10.3	.122	3.1	6.4	1.1	.24	6.0	1.5	6.7	.17	4.3	0.017	0.4	9.00	MW	C	N
0.156	3.96	B11-50	.41	10.3	.116	2.9	11	2.0												



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.156	3.96	2916	.56	14.3	.116	2.9	11	1.9	.28	7.2	3.0	13	.23	5.9	0.020	0.5	10.6	MW	C	Z
0.156	3.96	906	.56	14.3	.110	2.8	19	3.3	.24	6.0	4.5	20	.28	7.0	0.023	0.6	11.0	MW	C	Z
0.156	3.96	3923	.56	14.3	.106	2.7	26	4.5	.14	3.6	3.6	16	.26	6.7	0.025	0.6	10.5	SST	CG	N
0.156	3.96	3982	.56	14.3	.106	2.7	25	4.4	.22	5.5	5.4	24	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.156	3.96	10074	.56	14.3	.104	2.6	36	6.3	.17	4.2	6.0	27	.27	6.8	0.026	0.7	10.3	MW	CG	Z
0.156	3.96	A15-42	.56	14.3	.102	2.6	47	8.3	.14	3.6	6.7	30	.26	6.5	0.027	0.7	9.50	MW	CG	GI
0.156	3.96	L-75	.56	14.3	.082	2.1	178	31	.06	1.6	11	50	.44	11.3	0.037	0.9	11.0	SPR	C	N
0.156	3.96	11112	.59	15.1	.128	3.3	2.5	.44	.29	7.4	.74	3.3	.14	3.5	0.014	0.4	8.75	SST	C	N
0.156	3.96	EE-51	.59	15.1	.116	2.9	11	2.0	.26	6.6	3.0	13	.22	5.6	0.020	0.5	10.0	MW	C	Z
0.156	3.96	NN-66	.59	15.1	.110	2.8	14	2.5	.21	5.4	3.0	13	.31	7.9	0.023	0.6	12.5	SST	C	N
0.156	3.96	392	.63	15.9	.134	3.4	1.2	.21	.47	12	.57	2.5	.10	2.4	0.011	0.3	7.75	MW	C	Z
0.156	3.96	11404	.63	15.9	.130	3.3	2.3	.41	.40	10	.93	4.1	.12	3.0	0.013	0.3	8.00	MW	C	Z
0.156	3.96	GG-52	.63	15.9	.126	3.2	1.7	.30	.36	9.0	.61	2.7	.27	6.9	0.015	0.4	17.0	MW	C	N
0.156	3.96	10016	.63	15.9	.116	2.9	15	2.7	.20	5.0	3.0	13	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.156	3.96	GG-45	.63	15.9	.116	2.9	18	3.2	.16	4.2	3.0	13	.16	4.1	0.020	0.5	7.00	MW	C	N
0.156	3.96	S-704	.63	15.9	.112	2.8	11	2.0	.23	5.9	2.6	12	.30	7.7	0.022	0.6	12.8	SST	C	N
0.156	3.96	S-859	.63	15.9	.112	2.8	9.7	1.7	.27	6.8	2.6	12	.34	8.7	0.022	0.6	14.5	SST	C	N
0.156	3.96	S-1101	.63	15.9	.108	2.7	16	2.7	.22	5.5	3.4	15	.32	8.2	0.024	0.6	13.5	SST	CG	N
0.156	3.96	M-121	.66	16.7	.118	3.0	5.2	.91	.33	8.5	1.7	7.7	.32	8.2	0.019	0.5	16.0	MW	C	BO
0.156	3.96	B2-32	.67	17.1	.136	3.5	.39	.07	.52	13	.20	.89	.15	3.8	0.010	0.3	14.0	MW	C	N
0.156	3.96	U-17	.69	17.4	.126	3.2	1.9	.33	.45	12	.85	3.8	.23	5.7	0.015	0.4	14.0	SST	C	N
0.156	3.96	WW-23	.69	17.4	.124	3.1	1.9	.34	.39	9.9	.75	3.3	.30	7.5	0.016	0.4	17.5	SST	C	N
0.156	3.96	LL-82	.69	17.4	.118	3.0	7.9	1.4	.22	5.5	1.7	7.6	.21	5.3	0.019	0.5	10.0	SST	C	N
0.156	3.96	CC-90	.69	17.4	.116	2.9	6.1	1.1	.33	8.3	2.0	8.8	.30	7.6	0.020	0.5	15.0	SST	CG	N
0.156	3.96	S-1179	.69	17.4	.116	2.9	11	1.9	.19	4.8	2.0	8.8	.21	5.3	0.020	0.5	9.50	SST	C	N
0.156	3.96	H-57	.69	17.4	.112	2.8	11	1.9	.36	9.1	3.8	17	.33	8.4	0.022	0.6	15.0	MW	CG	N
0.156	3.96	LL-11	.69	17.4	.096	2.4	40	7.0	.15	3.9	6.1	27	.48	12.2	0.030	0.8	15.0	SST	C	N
0.156	3.96	W-34	.72	18.2	.118	3.0	3.8	.67	.37	9.3	1.4	6.3	.35	8.9	0.019	0.5	18.5	SST	CG	N
0.156	3.96	1837	.75	19.1	.140	3.6	.17	.03	.65	16	.11	.47	.10	2.6	0.008	0.2	13.0	MW	C	N
0.156	3.96	2505	.75	19.1	.136	3.5	.36	.06	.59	15	.21	.93	.16	4.1	0.010	0.3	15.0	MW	C	Z
0.156	3.96	PP-30	.75	19.1	.136	3.5	.31	.05	.57	14	.18	.78	.18	4.6	0.010	0.3	17.0	MW	C	N
0.156	3.96	JJ-84	.75	19.1	.124	3.1	2.5	.43	.48	12	1.2	5.2	.27	6.9	0.016	0.4	16.0	MW	C	GI
0.156	3.96	II-50	.75	19.1	.120	3.0	3.6	.63	.43	11	1.5	6.8	.32	8.2	0.018	0.5	18.0	MW	CG	Z
0.156	3.96	S-705	.75	19.1	.112	2.8	9.2	1.6	.29	7.3	2.6	12	.36	9.1	0.022	0.6	15.3	SST	C	N
0.156	3.96	KK-37	.75	19.1	.110	2.8	17	3.0	.26	6.7	4.5	20	.30	7.6	0.023	0.6	12.0	MW	C	GI
0.156	3.96	V-25	.81	20.6	.116	2.9	4.8	.84	.39	10	1.9	8.4	.42	10.7	0.020	0.5	21.0	MW	CG	Z
0.156	3.96	B7-6	.81	20.6	.116	2.9	5.0	.88	.39	9.8	1.9	8.6	.43	10.8	0.020	0.5	20.3	MW	C	Z
0.156	3.96	10313	.81	20.6	.100	2.5	26	4.6	.28	7.2	7.5	33	.50	12.8	0.028	0.7	18.0	MW	CG	GI
0.156	3.96	B15-67	.84	21.4	.132	3.4	.59	.10	.60	15	.35	1.6	.24	6.1	0.012	0.3	19.0	MW	C	N
0.156	3.96	CC-25	.88	22.2	.132	3.4	.74	.13	.68	17	.50	2.2	.20	5.0	0.012	0.3	15.5	MW	C	Z
0.156	3.96	II-45	.88	22.2	.132	3.4	.21	.04	.34	8.5	.07	.31	.54	13.7	0.012	0.3	44.0	SST	C	N
0.156	3.96	2658	.88	22.2	.130	3.3	.83	.14	.62	16	.51	2.3	.26	6.6	0.013	0.3	19.0	MW	C	GI
0.156	3.96	00-83	.88	22.2	.126	3.2	1.6	.28	.59	15	.96	4.3	.29	7.2	0.015	0.4	18.0	MW	C	N
0.156	3.96	3777	.88	22.2	.124	3.1	2.2	.39	.58	15	1.3	5.7	.30	7.5	0.016	0.4	17.5	MW	C	Z
0.156	3.96	V-31	.88	22.2	.118	3.0	3.4	.60	.47	12	1.6	7.1	.41	10.4	0.019	0.5	20.5	SST	C	N
0.156	3.96	1619	.88	22.2	.112	2.8	12	2.0	.34	8.6	3.9	18	.33	8.4	0.022	0.6	14.0	MW	C	Z
0.156	3.96	S-706	.88	22.2	.112	2.8	7.7	1.4	.34	8.6	2.6	12	.41	10.5	0.022	0.6	17.8	SST	C	N
0.156	3.96	00-17	.88	22.2	.096	2.4	45	7.8	.20	5.1	9.1	40	.48	12.2	0.030	0.8	15.0	MW	C	N
0.156	3.96	Y-48	.91	23.0	.106	2.7	21	3.6	.26	6.6	5.4	24	.38	9.5	0.025	0.6	14.0	MW	C	N
0.156	3.96	B15-20	.94	23.8	.102	2.6	27	4.8	.25	6.2	6.7	30	.41	10.3	0.027	0.7	15.0	MW	CG	Z
0.156	3.96	S-1165	.94	23.8	.096	2.4	25	4.4	.24	6.1	6.1	27	.66	16.8	0.030	0.8	22.0	SST	CG	N
0.156	3.96	393	1.00	25.4	.134	3.4	.73	.13	.78	20	.57	2.5	.14	3.5	0.011	0.3	11.5	MW	C	Z
0.156	3.96	356-A	1.00	25.4	.130	3.3	1.2	.22	.74	19	.93	4.1	.19	4.7	0.013	0.3	13.3	MW	C	Z
0.156	3.96	355-A	1.00	25.4	.128	3.3	1.6	.28	.72	18	1.2	5.1	.21	5.3	0.014	0.4	14.0	MW	C	Z
0.156	3.96	S-1025	1.00	25.4	.128	3.3	.99	.17	.72	18	.71	3.2	.28	7.1	0.014	0.4	19.0	SST	C	N
0.156	3.96	PP-7	1.00	25.4	.128	3.3	1.2	.21	.73	19	.88	3.9	.27	6.8	0.014	0.4	18.0	MW	C	N
0.156	3.96	157-A	1.00	25.4	.124	3.1	2.5	.45	.61	16	1.6	6.9	.26	6.7	0.016	0.4	15.5	MW	C	Z
0.156	3.96	TT-27	1.00	25.4	.124	3.1	1.4	.24	.55	14	.76	3.4	.45	11.4	0.016	0.4	27.0	MW	C	N
0.156	3.96	158-A	1.00	25.4	.100	2.5	23	4.0	.32	8.2	7.5	33	.60	15.1	0.028	0.7	20.3	MW	C	Z
0.156	3.96	2938	1.06	27.0	.136	3.5	.26	.04	.85	22										



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.156	3.96	157-C	1.75	44.5	.124	3.1	1.4	.25	1.1	28	1.6	6.9	.43	11.0	0.016	0.4	26.0	MW	C	Z
0.156	3.96	0-114	1.75	44.5	.102	2.6	9.8	1.7	.46	12	4.5	20	.93	23.7	0.027	0.7	33.5	SST	C	N
0.156	3.96	158-C	1.75	44.5	.100	2.5	13	2.2	.59	15	7.5	33	1.02	25.8	0.028	0.7	35.3	MW	C	Z
0.156	3.96	1575	2.88	73.0	.126	3.2	.25	.04	1.3	33	.32	1.4	1.59	40.4	0.015	0.4	105.0	MW	C	Z
0.156	3.96	10851	3.31	84.1	.110	2.8	3.7	.64	.82	21	3.0	13	1.02	26.0	0.023	0.6	43.5	SST	C	N
0.156	3.96	A10-63	3.75	95.3	.110	2.8	3.3	.57	.92	23	3.0	13	1.14	28.9	0.023	0.6	48.5	SST	C	N
0.158	4.01	10242	.75	19.1	.116	2.9	14	2.4	.25	6.4	3.4	15	.23	5.9	0.021	0.5	10.0	MW	C	Z
0.168	4.27	12749	.47	11.9	.120	3.0	21	3.7	.22	5.5	4.6	21	.25	6.4	0.024	0.6	9.50	MW	C	N
0.172	4.37	S-1093	.19	4.8	.152	3.9	1.2	.21	.13	3.4	.16	.70	.06	1.4	0.010	0.3	4.50	SST	C	N
0.172	4.37	L-80	.19	4.8	.140	3.6	8.3	1.4	.09	2.3	.76	3.4	.10	2.4	0.016	0.4	5.00	MW	C	N
0.172	4.37	M-31	.19	4.8	.114	2.9	103	18	.04	1.1	4.4	19	.15	3.7	0.029	0.7	5.00	SST	CG	N
0.172	4.37	BB-45	.22	5.6	.136	3.5	13	2.3	.10	2.5	1.3	5.9	.09	2.2	0.018	0.5	4.75	SST	CG	N
0.172	4.37	KK-23	.25	6.4	.144	3.7	5.6	.98	.17	4.4	.97	4.3	.08	2.0	0.014	0.4	4.50	MW	C	N
0.172	4.37	B5-8	.25	6.4	.140	3.6	9.9	1.7	.14	3.6	1.4	6.3	.07	1.8	0.016	0.4	4.50	MW	CG	N
0.172	4.37	CC-37	.25	6.4	.132	3.4	16	2.8	.11	2.8	1.8	8.1	.13	3.3	0.020	0.5	5.50	SST	C	N
0.172	4.37	B-17	.25	6.4	.116	2.9	64	11	.05	1.4	3.5	15	.20	5.0	0.028	0.7	6.00	SST	C	N
0.172	4.37	J-43	.25	6.4	.116	2.9	118	21	.06	1.5	6.9	30	.15	3.9	0.028	0.7	4.50	MW	C	N
0.172	4.37	AA-77	.25	6.4	.112	2.8	136	24	.06	1.6	8.4	37	.18	4.6	0.030	0.8	5.00	MW	C	Z
0.172	4.37	NN-82	.28	7.1	.156	4.0	.24	.04	.21	5.4	.05	.23	.07	1.7	0.008	0.2	7.50	MW	C	N
0.172	4.37	Y-92	.28	7.1	.136	3.5	12	2.1	.16	4.2	1.9	8.6	.12	3.0	0.018	0.5	5.50	MW	C	N
0.172	4.37	W-1	.28	7.1	.108	2.7	136	24	.05	1.3	6.7	30	.18	4.5	0.032	0.8	5.50	SST	CG	N
0.172	4.37	A9-24	.31	7.9	.148	3.8	3.6	.64	.18	4.7	.67	3.0	.06	1.5	0.012	0.3	4.00	MW	C	N
0.172	4.37	00-38	.31	7.9	.148	3.8	1.5	.25	.23	5.8	.33	1.5	.08	2.1	0.012	0.3	7.00	MW	CG	N
0.172	4.37	A14-10	.31	7.9	.140	3.6	8.3	1.4	.17	4.4	1.4	6.3	.08	2.0	0.016	0.4	5.00	MW	CG	N
0.172	4.37	S-1202	.31	7.9	.128	3.3	17	3.0	.14	3.5	2.4	10	.18	4.5	0.022	0.6	7.00	SST	C	N
0.172	4.37	A11-22	.31	7.9	.126	3.2	32	5.7	.13	3.2	4.1	18	.13	3.4	0.023	0.6	5.75	MW	CG	GI
0.172	4.37	A15-19	.34	8.7	.140	3.6	6.2	1.1	.23	5.8	1.4	6.3	.11	2.8	0.016	0.4	6.00	MW	C	N
0.172	4.37	B18-127	.34	8.7	.136	3.5	6.9	1.2	.22	5.5	1.5	6.6	.13	3.2	0.018	0.5	6.00	MW	O	N
0.172	4.37	10768	.34	8.7	.122	3.1	51	8.8	.10	2.5	4.9	22	.16	4.1	0.025	0.6	5.50	MW	C	N
0.172	4.37	N-301	.34	8.7	.120	3.0	62	11	.06	1.5	3.7	16	.16	4.0	0.026	0.7	5.00	SST	C	N
0.172	4.37	GG-37	.34	8.7	.102	2.6	122	21	.06	1.6	7.7	34	.28	7.1	0.035	0.9	8.00	SST	CG	N
0.172	4.37	12654	.34	8.7	.142	3.6	4.7	.82	.24	6.1	1.1	5.0	.11	2.7	0.015	0.4	6.00	MW	C	N
0.172	4.37	00-30	.38	9.5	.148	3.8	1.1	.18	.27	6.8	.28	1.3	.11	2.7	0.012	0.3	8.00	SST	C	N
0.172	4.37	JJ-41	.38	9.5	.138	3.5	6.4	1.1	.24	6.1	1.5	6.9	.14	3.5	0.017	0.4	7.00	MW	C	Z
0.172	4.37	JJ-50	.38	9.5	.132	3.4	15	2.5	.13	3.2	1.8	8.1	.14	3.6	0.020	0.5	6.00	SST	C	N
0.172	4.37	0-71	.38	9.5	.132	3.4	13	2.3	.21	5.3	2.7	12	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.172	4.37	AA-3	.38	9.5	.122	3.1	44	7.7	.11	2.8	4.9	22	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.172	4.37	DD-2	.38	9.5	.108	2.7	96	17	.07	1.8	6.7	30	.22	5.7	0.032	0.8	7.00	SST	CG	N
0.172	4.37	J-95	.41	10.3	.142	3.6	2.4	.41	.24	6.1	.57	2.5	.17	4.2	0.015	0.4	10.0	MW	C	Z
0.172	4.37	NN-18	.41	10.3	.142	3.6	2.5	.44	.26	6.7	.66	2.9	.14	3.6	0.015	0.4	9.50	MW	CG	N
0.172	4.37	NN-63	.41	10.3	.126	3.2	20	3.5	.20	5.1	4.0	18	.21	5.3	0.023	0.6	8.00	MW	C	N
0.172	4.37	B5-21	.41	10.3	.120	3.0	42	7.4	.13	3.3	5.5	25	.21	5.3	0.026	0.7	7.00	MW	C	N
0.172	4.37	B-56	.41	10.3	.116	2.9	66	11	.07	1.8	4.6	20	.20	5.0	0.028	0.7	6.00	SST	C	N
0.172	4.37	EE-85	.41	10.3	.112	2.8	74	13	.11	2.9	8.4	37	.26	6.5	0.030	0.8	7.50	MW	C	N
0.172	4.37	J-3	.41	10.3	.096	2.4	208	36	.05	1.4	11	50	.30	7.7	0.038	1.0	8.00	SPR	CG	Z
0.172	4.37	12642	.42	10.7	.112	2.8	59	10	.09	2.4	5.6	25	.24	6.1	0.030	0.8	8.00	SST	CG	N
0.172	4.37	S-1463	.44	11.1	.160	4.1	.06	.01	.38	9.8	.02	.10	.05	1.4	0.006	0.2	8.00	SST	C	N
0.172	4.37	I-6	.44	11.1	.152	3.9	.16	.03	.20	5.0	.03	.14	.24	6.1	0.010	0.3	23.0	MW	C	BO
0.172	4.37	3795	.44	11.1	.144	3.7	2.0	.35	.31	7.9	.62	2.8	.13	3.2	0.014	0.4	9.00	MW	CG	Z
0.172	4.37	JJ-66	.44	11.1	.136	3.5	3.4	.60	.21	5.4	.73	3.2	.23	5.7	0.018	0.5	12.5	SST	CG	N
0.172	4.37	B5-5	.44	11.1	.136	3.5	7.2	1.3	.28	7.1	2.0	8.9	.16	4.0	0.018	0.5	7.75	MW	C	N
0.172	4.37	NN-23	.44	11.1	.134	3.4	11	2.0	.14	3.5	1.6	7.0	.13	3.4	0.019	0.5	6.00	SST	C	N
0.172	4.37	FF-74	.44	11.1	.132	3.4	9.4	1.6	.24	6.0	2.2	9.9	.20	5.1	0.020	0.5	9.00	MW	C	Z
0.172	4.37	M-1	.44	11.1	.132	3.4	8.2	1.4	.22	5.5	1.8	7.9	.22	5.6	0.020	0.5	10.0	MW	C	Z
0.172	4.37	00-65	.44	11.1	.132	3.4	14	2.5	.19	4.9	2.7	12	.22	5.6	0.020	0.5	9.00	MW	C	Z
0.172	4.37	U-57	.44	11.1	.132	3.4	11	2.0	.16	4.1	1.8	8.1	.16	4.1	0.020	0.5	7.00	SST	C	N
0.172	4.37	V-47	.44	11.1	.132	3.4	4.8	.85	.14	3.5	.67	3.0	.30	7.6	0.020	0.5	14.0	SST	C	N
0.172	4.37	A14-2	.44	11.1	.122	3.1	26	4.6	.13	3.2	3.3	15	.20	5.1	0.025	0.6	8.00	SST	CG	N
0.172	4.37	AA-45	.44	11.1	.118	3.0	44	7.6	.09	2.4	4.1	18	.22							




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.172	4.37	A14-24	.53	13.5	.108	2.7	65	11	.16	3.9	10	45	.34	8.5	0.032	0.8	10.5	MW	CG	GI
0.172	4.37	S-332	.56	14.3	.152	3.9	.27	.05	.42	11	.11	.50	.14	3.6	0.010	0.3	13.0	SST	C	N
0.172	4.37	CC-41	.56	14.3	.148	3.8	.37	.07	.32	8.2	.12	.53	.24	6.1	0.012	0.3	19.0	SST	C	N
0.172	4.37	DD-19	.56	14.3	.148	3.8	.97	.17	.44	11	.42	1.9	.13	3.2	0.012	0.3	9.50	MW	C	N
0.172	4.37	B-8	.56	14.3	.132	3.4	4.6	.80	.25	6.4	1.1	5.1	.31	7.9	0.020	0.5	14.5	SST	C	N
0.172	4.37	K-75	.56	14.3	.120	3.0	22	3.9	.24	6.0	5.3	23	.33	8.3	0.026	0.7	11.5	MW	C	N
0.172	4.37	F-17	.56	14.3	.120	3.0	26	4.6	.21	5.3	5.5	25	.29	7.3	0.026	0.7	10.0	MW	C	Z
0.172	4.37	S-142	.56	14.3	.108	2.7	48	8.4	.14	3.6	6.7	30	.38	9.8	0.032	0.8	12.0	SST	CG	N
0.172	4.37	S-900	.59	15.1	.156	4.0	.13	.02	.50	13	.07	.30	.09	2.4	0.008	0.2	10.7	SST	C	N
0.172	4.37	10265	.59	15.1	.152	3.9	.56	.10	.50	13	.28	1.3	.09	2.3	0.010	0.3	8.00	MW	C	N
0.172	4.37	B15-47	.59	15.1	.136	3.5	5.2	.90	.39	9.9	2.0	8.9	.20	5.0	0.018	0.5	10.0	MW	C	N
0.172	4.37	U-96	.59	15.1	.132	3.4	8.2	1.4	.33	8.5	2.7	12	.20	5.1	0.020	0.5	10.0	MW	CG	N
0.172	4.37	FF-39	.59	15.1	.120	3.0	16	2.7	.21	5.3	3.3	15	.38	9.7	0.026	0.7	13.8	SST	C	N
0.172	4.37	S-487	.59	15.1	.114	2.9	30	5.3	.17	4.3	5.1	23	.38	9.6	0.029	0.7	12.0	SST	C	N
0.172	4.37	W-67	.59	15.1	.088	2.2	226	40	.07	1.7	15	65	.46	11.7	0.042	1.1	11.0	SPR	CG	N
0.172	4.37	L-28	.63	15.9	.144	3.7	1.2	.20	.42	11	.48	2.2	.21	5.3	0.014	0.4	14.0	MW	C	N
0.172	4.37	A14-18	.63	15.9	.136	3.5	6.7	1.2	.20	5.1	1.3	5.9	.14	3.4	0.018	0.5	7.50	SST	CG	N
0.172	4.37	S-835	.63	15.9	.136	3.5	2.8	.48	.34	8.6	.93	4.1	.29	7.3	0.018	0.5	15.0	SST	C	N
0.172	4.37	J-44	.63	15.9	.128	3.3	14	2.5	.25	6.4	3.6	16	.22	5.6	0.022	0.6	9.00	MW	C	Z
0.172	4.37	AA-65	.63	15.9	.122	3.1	14	2.4	.23	5.7	3.1	14	.40	10.2	0.025	0.6	15.0	MW	C	Z
0.172	4.37	A15-17	.63	15.9	.120	3.0	23	4.1	.24	6.0	5.5	25	.29	7.3	0.026	0.7	11.0	MW	CG	N
0.172	4.37	2520	.63	15.9	.118	3.0	36	6.3	.17	4.4	6.2	27	.27	6.9	0.027	0.7	9.00	MW	C	Z
0.172	4.37	N-109	.63	15.9	.112	2.8	37	6.5	.15	3.8	5.6	25	.35	8.8	0.030	0.8	11.5	SST	CG	N
0.172	4.37	B5-4	.66	16.7	.130	3.3	8.8	1.5	.36	9.1	3.2	14	.24	6.0	0.021	0.5	11.3	MW	CG	N
0.172	4.37	S-220	.66	16.7	.120	3.0	14	2.5	.24	6.1	3.4	15	.42	10.6	0.026	0.7	15.0	SST	C	N
0.172	4.37	DD-58	.66	16.7	.112	2.8	52	9.0	.11	2.8	5.6	25	.27	6.9	0.030	0.8	9.00	SST	CG	N
0.172	4.37	FF-38	.66	16.7	.112	2.8	34	6.0	.16	4.1	5.6	25	.38	9.5	0.030	0.8	12.5	SST	CG	N
0.172	4.37	S-1227	.69	17.4	.132	3.4	3.4	.59	.29	7.3	.96	4.3	.40	10.2	0.020	0.5	19.0	SST	C	N
0.172	4.37	BB-33	.69	17.4	.132	3.4	3.8	.66	.33	8.3	1.2	5.5	.36	9.1	0.020	0.5	17.0	SST	C	N
0.172	4.37	11364	.69	17.4	.132	3.4	5.3	.92	.34	8.7	1.8	8.1	.28	7.1	0.020	0.5	13.0	SST	C	N
0.172	4.37	FF-17	.69	17.4	.128	3.3	11	1.9	.22	5.6	2.4	11	.24	6.1	0.022	0.6	10.0	SST	C	N
0.172	4.37	L-93	.72	18.2	.128	3.3	8.1	1.4	.38	9.7	3.1	14	.34	8.5	0.022	0.6	14.3	MW	C	Z
0.172	4.37	B7-48	.72	18.2	.122	3.1	17	3.0	.29	7.3	4.9	22	.31	7.8	0.025	0.6	12.3	MW	CG	N
0.172	4.37	B-13	.72	18.2	.120	3.0	16	2.8	.23	5.9	3.7	16	.38	9.6	0.026	0.7	13.5	SST	C	N
0.172	4.37	PP-22	.72	18.2	.098	2.5	108	19	.09	2.3	9.7	43	.44	11.3	0.037	0.9	11.0	SST	C	N
0.172	4.37	PP-26	.75	19.1	.156	4.0	.13	.02	.65	16	.09	.38	.10	2.6	0.008	0.2	12.0	MW	C	N
0.172	4.37	WW-31	.75	19.1	.146	3.7	.89	.16	.58	15	.52	2.3	.17	4.3	0.013	0.3	12.0	SST	C	N
0.172	4.37	S-1069	.75	19.1	.144	3.7	.87	.15	.51	13	.45	2.0	.24	6.0	0.014	0.4	16.0	SST	C	N
0.172	4.37	11457	.75	19.1	.144	3.7	1.6	.27	.43	11	.67	3.0	.15	3.9	0.014	0.4	10.0	SST	C	N
0.172	4.37	O-110	.75	19.1	.142	3.6	2.4	.41	.50	13	1.2	5.2	.15	3.8	0.015	0.4	10.0	MW	CG	N
0.172	4.37	3582	.75	19.1	.140	3.6	2.3	.40	.53	13	1.2	5.3	.22	5.7	0.016	0.4	13.0	MW	C	GI
0.172	4.37	MM-21	.75	19.1	.140	3.6	1.8	.31	.51	13	.90	4.0	.24	6.1	0.016	0.4	14.0	MW	O	Z
0.172	4.37	KK-15	.75	19.1	.132	3.4	6.7	1.2	.27	6.9	1.8	8.1	.23	5.8	0.020	0.5	10.5	SST	C	N
0.172	4.37	A12-26	.75	19.1	.132	3.4	5.5	.96	.45	11	2.5	11	.30	7.6	0.020	0.5	14.0	MW	C	Z
0.172	4.37	B-75	.75	19.1	.130	3.3	8.1	1.4	.39	9.9	3.2	14	.27	6.9	0.021	0.5	12.0	MW	C	Z
0.172	4.37	J-93	.75	19.1	.090	2.3	139	24	.10	2.5	14	61	.62	15.6	0.041	1.0	15.0	SPR	CG	N
0.172	4.37	AA-29	.78	19.8	.152	3.9	.38	.07	.66	17	.25	1.1	.12	3.0	0.010	0.3	11.0	MW	C	Z
0.172	4.37	A15-11	.78	19.8	.140	3.6	3.1	.54	.46	12	1.4	6.3	.18	4.5	0.016	0.4	10.0	MW	C	N
0.172	4.37	B10-38	.81	20.6	.152	3.9	.29	.05	.67	17	.20	.87	.15	3.7	0.010	0.3	13.5	MW	C	N
0.172	4.37	W-36	.84	21.4	.110	2.8	43	7.5	.21	5.4	9.2	41	.43	11.0	0.031	0.8	13.0	MW	C	N
0.172	4.37	G-56	.88	22.2	.142	3.6	1.3	.24	.62	16	.83	3.7	.26	6.5	0.015	0.4	16.0	MW	C	N
0.172	4.37	1829	.88	22.2	.140	3.6	1.8	.31	.60	15	1.1	4.8	.27	6.9	0.016	0.4	16.0	MW	C	Z
0.172	4.37	B-59	.88	22.2	.138	3.5	2.3	.40	.59	15	1.3	6.0	.29	7.3	0.017	0.4	16.0	MW	C	N
0.172	4.37	G-38	.88	22.2	.130	3.3	4.8	.84	.46	12	2.2	9.7	.42	10.7	0.021	0.5	19.0	MW	C	Z
0.172	4.37	10186	.88	22.2	.128	3.3	8.3	1.5	.43	11	3.6	16	.33	8.4	0.022	0.6	14.0	MW	C	Z
0.172	4.37	V-56	.88	22.2	.128	3.3	5.9	1.0	.44	11	2.6	11	.44	11.2	0.022	0.6	19.0	MW	C	N
0.172	4.37	S-1693	.89	22.6	.124	3.1	9.8	1.7	.31	8.0	3.1	14	.36	9.1	0.024	0.6	15.0	SST	CG	N
0.172	4.37	00-42	.94	23.8	.140	3.6	2.1	.36	.69	17	1.4	6.3	.24	6.1	0.016	0.4	14.0	MW	C	Z
0.172	4.37	Z-79	.94	23.8	.108	2.7	37	6.4	.18	4.7	6.7	30	.51	13.0	0.032	0.8	15.0	SST	C	N
0.172	4.37	J-9	1.00	25.4	.150	3.8	.27	.05	.79	20	.22	.96	.21	5.3	0.011	0.3	18.0	SST	C	N
0.172	4.37	00-81	1.00	25.4	.148	3.8	.73	.13	.84	21	.61	2.7	.16	4.0	0.012	0.3	12.0	MW	C	BO
0.172	4.37	S-1077	1.00	25.4	.136	3.5	3.6	.63	.37	9.4	1.3	5.9	.23	5.9	0.018	0.5	12.0	SST	C	N
0.172	4.37	S-1346	1.00	25.4	.132	3.4	4.4	.77	.41	11	1.8	8.1	.32	8.1	0.020	0.5	15.0	SST	C	N
0.172	4.37	A12-28	1.00	25.4	.120	3.0	13	2.3	.42	11	5.5	25	.49	12.5	0.026	0.7	18.0	MW	C	N
0.172	4.37	B2-36	1.00	25.4	.118	3.0	24	4.2	.26	6.6	6.2	27	.37	9.3	0.027	0.7	12.5	MW	C	Z
0.172	4.37	10635	1.00	25.4	.102	2.6	59	10	.15	3.8	8.9	40	.60	15.3	0.035	0.9	16.3	SPR	C	N
0.172	4.37	GG-31	1.06	27.0	.108	2.7	27	4.7	.27	6.9	7.2	32	.72	18.3	0.032	0.8	22.5	SPR	CG	N
0.172	4.37	A15-12	1.09	27.8	.106	2.7	39	6.8	.19	4.8	7.3	33	.54	13.8	0.033	0.8	16.5	SST	CG	N
0.172	4.37	JJ-31	1.09	27.8	.102	2.6	37	6.6	.22	5.7	8.3	37	.75	19.1	0.035	0.9	21.5	SST	CG	N</



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.172	4.37	Q-79	1.38	34.9	.142	3.6	.72	.13	.94	24	.68	3.0	.44	11.0	0.015	0.4	28.0	MW	C	N
0.172	4.37	LL-74	1.50	38.1	.128	3.3	3.1	.54	.77	20	2.4	11	.68	17.3	0.022	0.6	30.0	SST	C	N
0.172	4.37	10261	1.56	39.7	.122	3.1	5.9	1.0	.74	19	4.3	19	.83	21.0	0.025	0.6	32.0	MW	C	Z
0.172	4.37	10859	1.75	44.5	.102	2.6	39	6.9	.21	5.4	8.3	37	.74	18.7	0.035	0.9	21.0	SST	CG	N
0.172	4.37	Y-61	1.94	49.2	.136	3.5	.92	.16	1.2	30	1.1	4.8	.76	19.2	0.018	0.5	41.0	SST	C	N
0.172	4.37	B15-41	2.25	57.2	.156	4.0	.07	.01	2.1	53	.15	.69	.17	4.3	0.008	0.2	20.0	MW	C	N
0.172	4.37	B18-185	2.50	63.5	.122	3.1	5.1	.88	.98	25	4.9	22	.93	23.5	0.025	0.6	37.0	MW	CG	Z
0.172	4.37	Y-64	2.75	69.9	.116	2.9	4.3	.75	.99	25	4.2	19	1.76	44.8	0.028	0.7	62.0	SST	C	N
0.172	4.37	S-3214	2.91	73.8	.134	3.4	1.1	.18	1.5	38	1.6	7.0	.89	22.7	0.019	0.5	46.0	SST	O	N
0.172	4.37	3968	3.00	76.2	.118	3.0	4.3	.75	1.3	34	5.7	26	1.66	42.2	0.027	0.7	60.5	MW	C	N
0.172	4.37	B15-44	3.19	81.0	.146	3.7	.33	.06	2.6	65	.85	3.8	.44	11.2	0.013	0.3	33.0	MW	C	N
0.172	4.37	FF-48	3.25	82.6	.152	3.9	.08	.01	2.8	72	.24	1.1	.43	10.9	0.010	0.3	42.0	MW	C	N
0.175	4.45	B3-49	.47	11.9	.103	2.6	98	17	.09	2.3	8.9	40	.36	9.1	0.036	0.9	10.0	SST	CG	N
0.180	4.57	70244	.25	6.4	.156	4.0	3.6	.63	.18	4.5	.64	2.8	.05	1.1	0.012	0.3	3.75	MW	CG	N
0.180	4.57	70244S	.25	6.4	.156	4.0	3.1	.55	.13	3.3	.41	1.8	.05	1.1	0.012	0.3	3.75	SST	CG	N
0.180	4.57	70259	.25	6.4	.152	3.9	6.0	1.1	.17	4.2	1.0	4.5	.06	1.4	0.014	0.4	4.00	MW	CG	N
0.180	4.57	70259S	.25	6.4	.152	3.9	5.2	.92	.12	3.1	.64	2.9	.06	1.4	0.014	0.4	4.00	SST	CG	N
0.180	4.57	70280	.25	6.4	.148	3.8	9.0	1.6	.15	3.9	1.4	6.0	.07	1.8	0.016	0.4	4.38	MW	CG	N
0.180	4.57	70280S	.25	6.4	.148	3.8	7.6	1.3	.12	3.0	.90	4.0	.07	1.8	0.016	0.4	4.38	SST	CG	N
0.180	4.57	70301	.25	6.4	.144	3.7	14	2.4	.14	3.6	1.9	8.5	.08	2.1	0.018	0.5	4.63	MW	CG	N
0.180	4.57	70301S	.25	6.4	.144	3.7	11	2.0	.11	2.8	1.3	5.7	.08	2.1	0.018	0.5	4.63	SST	CG	N
0.180	4.57	70322	.25	6.4	.140	3.6	21	3.7	.12	3.2	2.6	12	.09	2.3	0.020	0.5	4.63	MW	CG	N
0.180	4.57	70322S	.25	6.4	.140	3.6	18	3.1	.10	2.5	1.7	7.7	.09	2.3	0.020	0.5	4.63	SST	CG	N
0.180	4.57	70343	.25	6.4	.136	3.5	30	5.2	.12	3.0	3.5	15	.11	2.7	0.022	0.6	4.88	MW	CG	N
0.180	4.57	70343S	.25	6.4	.136	3.5	25	4.4	.09	2.3	2.3	10	.11	2.7	0.022	0.6	4.88	SST	CG	N
0.180	4.57	A12-37	.25	6.4	.136	3.5	30	5.2	.08	2.0	2.3	10	.10	2.5	0.022	0.6	4.50	SST	CG	N
0.180	4.57	70363	.25	6.4	.132	3.4	43	7.6	.10	2.6	4.5	20	.12	3.0	0.024	0.6	4.88	MW	CG	N
0.180	4.57	70363S	.25	6.4	.132	3.4	37	6.4	.08	2.1	3.0	13	.12	3.0	0.024	0.6	4.88	SST	CG	N
0.180	4.57	70386	.25	6.4	.128	3.3	59	10	.09	2.3	5.3	24	.13	3.3	0.026	0.7	5.00	MW	CG	N
0.180	4.57	70386S	.25	6.4	.128	3.3	50	8.8	.07	1.8	3.6	16	.13	3.3	0.026	0.7	5.00	SST	CG	N
0.180	4.57	70407	.25	6.4	.122	3.1	95	17	.08	1.9	7.3	32	.15	3.8	0.029	0.7	5.13	MW	CG	N
0.180	4.57	70407S	.25	6.4	.122	3.1	81	14	.06	1.5	4.9	22	.15	3.8	0.029	0.7	5.13	SST	CG	N
0.180	4.57	B4-67	.30	7.5	.152	3.9	2.8	.50	.20	5.0	.55	2.5	.10	2.6	0.014	0.4	6.25	MW	C	N
0.180	4.57	70245	.31	7.9	.156	4.0	3.0	.52	.22	5.5	.64	2.8	.05	1.3	0.012	0.3	4.13	MW	CG	N
0.180	4.57	70245S	.31	7.9	.156	4.0	2.6	.45	.16	4.0	.41	1.8	.05	1.3	0.012	0.3	4.13	SST	CG	N
0.180	4.57	70260	.31	7.9	.152	3.9	4.8	.85	.21	5.3	1.0	4.5	.06	1.6	0.014	0.4	4.50	MW	CG	N
0.180	4.57	70260S	.31	7.9	.152	3.9	4.2	.74	.15	3.9	.64	2.9	.06	1.6	0.014	0.4	4.50	SST	CG	N
0.180	4.57	70281	.31	7.9	.148	3.8	7.5	1.3	.18	4.6	1.4	6.0	.08	2.0	0.016	0.4	4.88	MW	CG	N
0.180	4.57	70281S	.31	7.9	.148	3.8	6.4	1.1	.14	3.6	.90	4.0	.08	2.0	0.016	0.4	4.88	SST	CG	N
0.180	4.57	70302	.31	7.9	.144	3.7	11	2.0	.17	4.4	1.9	8.5	.09	2.3	0.018	0.5	5.13	MW	CG	N
0.180	4.57	70302S	.31	7.9	.144	3.7	9.5	1.7	.13	3.4	1.3	5.7	.09	2.3	0.018	0.5	5.13	SST	CG	N
0.180	4.57	70323	.31	7.9	.140	3.6	16	2.8	.16	4.1	2.6	12	.11	2.8	0.020	0.5	5.50	MW	CG	N
0.180	4.57	70323S	.31	7.9	.140	3.6	14	2.4	.13	3.2	1.7	7.7	.11	2.8	0.020	0.5	5.50	SST	CG	N
0.180	4.57	70344	.31	7.9	.136	3.5	24	4.2	.15	3.7	3.5	15	.12	3.1	0.022	0.6	5.63	MW	CG	N
0.180	4.57	70344S	.31	7.9	.136	3.5	20	3.6	.11	2.9	2.3	10	.12	3.1	0.022	0.6	5.63	SST	CG	N
0.180	4.57	70364	.31	7.9	.132	3.4	33	5.7	.14	3.5	4.5	20	.14	3.6	0.024	0.6	5.88	MW	CG	N
0.180	4.57	70364S	.31	7.9	.132	3.4	28	4.9	.11	2.7	3.0	13	.14	3.6	0.024	0.6	5.88	SST	CG	N
0.180	4.57	70387	.31	7.9	.128	3.3	47	8.2	.11	2.9	5.3	24	.15	3.9	0.026	0.7	5.88	MW	CG	N
0.180	4.57	70387S	.31	7.9	.128	3.3	40	7.0	.09	2.3	3.6	16	.15	3.9	0.026	0.7	5.88	SST	CG	N
0.180	4.57	70408	.31	7.9	.122	3.1	74	13	.10	2.5	7.3	32	.17	4.4	0.029	0.7	6.00	MW	CG	N
0.180	4.57	70408S	.31	7.9	.122	3.1	62	11	.08	2.0	4.9	22	.17	4.4	0.029	0.7	6.00	SST	CG	N
0.180	4.57	70426	.31	7.9	.116	2.9	122	21	.08	2.0	9.7	43	.18	4.7	0.032	0.8	5.75	MW	CG	N
0.180	4.57	70426S	.31	7.9	.116	2.9	104	18	.06	1.6	6.5	29	.18	4.7	0.032	0.8	5.75	SST	CG	N
0.180	4.57	70246	.38	9.7	.156	4.0	2.3	.40	.28	7.1	.64	2.8	.06	1.4	0.012	0.3	4.75	MW	CG	N
0.180	4.57	70246S	.38	9.7	.156	4.0	2.0	.35	.20	5.2	.41	1.8	.06	1.4	0.012	0.3	4.75	SST	CG	N
0.180	4.57	70261	.38	9.7	.152	3.9	3.9	.68	.26	6.6	1.0	4.5	.07	1.8	0.014	0.4	5.13	MW	CG	N
0.180	4.57	70261S	.38	9.7	.152	3.9	3.4	.59	.19	4.9	.64	2.9	.07	1.8	0.014	0.4	5.13	SST	CG	N
0.180	4.57	70282	.38	9.7	.148	3.8	6.0	1.0	.23	5.8	1.4	6.0	.09	2.3	0.016	0.4	5.63	MW	CG	N
0.180	4.57	70282S</																		



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70283S	.44	11.2	.148	3.8	4.2	.74	.21	5.4	.90	4.0	.10	2.6	0.016	0.4	6.38	SST	CG	N
0.180	4.57	70304	.44	11.2	.144	3.7	7.9	1.4	.24	6.2	1.9	8.5	.12	3.0	0.018	0.5	6.50	MW	CG	N
0.180	4.57	70304S	.44	11.2	.144	3.7	6.7	1.2	.19	4.8	1.3	5.7	.12	3.0	0.018	0.5	6.50	SST	CG	N
0.180	4.57	70325	.44	11.2	.140	3.6	11	1.9	.24	6.0	2.6	12	.14	3.6	0.020	0.5	7.13	MW	CG	N
0.180	4.57	70325S	.44	11.2	.140	3.6	9.4	1.6	.19	4.7	1.7	7.7	.14	3.6	0.020	0.5	7.13	SST	CG	N
0.180	4.57	70346	.44	11.2	.136	3.5	17	3.0	.20	5.2	3.5	15	.15	3.9	0.022	0.6	7.00	MW	CG	N
0.180	4.57	70346S	.44	11.2	.136	3.5	14	2.5	.16	4.1	2.3	10	.15	3.9	0.022	0.6	7.00	SST	CG	N
0.180	4.57	70366	.44	11.2	.132	3.4	22	3.8	.20	5.2	4.5	20	.19	4.7	0.024	0.6	7.75	MW	CG	N
0.180	4.57	70366S	.44	11.2	.132	3.4	19	3.3	.16	4.1	3.0	13	.19	4.7	0.024	0.6	7.75	SST	CG	N
0.180	4.57	70389	.44	11.2	.128	3.3	31	5.4	.17	4.3	5.3	24	.20	5.1	0.026	0.7	7.75	MW	CG	N
0.180	4.57	70389S	.44	11.2	.128	3.3	26	4.6	.13	3.4	3.6	16	.20	5.1	0.026	0.7	7.75	SST	CG	N
0.180	4.57	70410	.44	11.2	.122	3.1	48	8.5	.15	3.8	7.3	32	.24	6.0	0.029	0.7	8.13	MW	CG	N
0.180	4.57	70410S	.44	11.2	.122	3.1	41	7.2	.12	3.0	4.9	22	.24	6.0	0.029	0.7	8.13	SST	CG	N
0.180	4.57	70428	.44	11.2	.116	2.9	79	14	.12	3.1	9.7	43	.25	6.4	0.032	0.8	7.88	MW	CG	N
0.180	4.57	70428S	.44	11.2	.116	2.9	67	12	.10	2.5	6.5	29	.25	6.4	0.032	0.8	7.88	SST	CG	N
0.180	4.57	70445	.44	11.2	.110	2.8	115	20	.10	2.6	12	53	.28	7.2	0.035	0.9	8.13	MW	CG	N
0.180	4.57	70445S	.44	11.2	.110	2.8	97	17	.08	2.1	8.0	36	.28	7.2	0.035	0.9	8.13	SST	CG	N
0.180	4.57	70248	.50	12.7	.156	4.0	1.7	.29	.38	9.7	.64	2.8	.07	1.8	0.012	0.3	5.75	MW	CG	N
0.180	4.57	70248S	.50	12.7	.156	4.0	1.5	.26	.28	7.1	.41	1.8	.07	1.8	0.012	0.3	5.75	SST	CG	N
0.180	4.57	70263	.50	12.7	.152	3.9	2.8	.50	.35	9.0	1.0	4.5	.09	2.2	0.014	0.4	6.25	MW	CG	N
0.180	4.57	70263S	.50	12.7	.152	3.9	2.5	.43	.26	6.6	.64	2.9	.09	2.2	0.014	0.4	6.25	SST	CG	N
0.180	4.57	70284	.50	12.7	.148	3.8	4.4	.76	.31	7.9	1.4	6.0	.11	2.8	0.016	0.4	6.88	MW	CG	N
0.180	4.57	70284S	.50	12.7	.148	3.8	3.7	.65	.24	6.2	.90	4.0	.11	2.8	0.016	0.4	6.88	SST	CG	N
0.180	4.57	70305	.50	12.7	.144	3.7	6.9	1.2	.28	7.1	1.9	8.5	.13	3.3	0.018	0.5	7.13	MW	CG	N
0.180	4.57	70305S	.50	12.7	.144	3.7	5.8	1.0	.22	5.6	1.3	5.7	.13	3.3	0.018	0.5	7.13	SST	CG	N
0.180	4.57	70326	.50	12.7	.140	3.6	9.5	1.7	.28	7.0	2.6	12	.16	4.0	0.020	0.5	7.88	MW	CG	N
0.180	4.57	70326S	.50	12.7	.140	3.6	8.1	1.4	.22	5.5	1.7	7.7	.16	4.0	0.020	0.5	7.88	SST	CG	N
0.180	4.57	70347	.50	12.7	.136	3.5	14	2.5	.25	6.2	3.5	15	.18	4.5	0.022	0.6	8.00	MW	CG	N
0.180	4.57	70347S	.50	12.7	.136	3.5	12	2.1	.19	4.9	2.3	10	.18	4.5	0.022	0.6	8.00	SST	CG	N
0.180	4.57	70367	.50	12.7	.132	3.4	19	3.3	.24	6.0	4.5	20	.21	5.3	0.024	0.6	8.63	MW	CG	N
0.180	4.57	70367S	.50	12.7	.132	3.4	16	2.8	.18	4.7	3.0	13	.21	5.3	0.024	0.6	8.63	SST	CG	N
0.180	4.57	70390	.50	12.7	.128	3.3	27	4.7	.20	5.0	5.3	24	.22	5.7	0.026	0.7	8.63	MW	CG	N
0.180	4.57	70390S	.50	12.7	.128	3.3	23	4.0	.16	4.0	3.6	16	.22	5.7	0.026	0.7	8.63	SST	CG	N
0.180	4.57	70411	.50	12.7	.122	3.1	42	7.3	.17	4.4	7.3	32	.26	6.7	0.029	0.7	9.13	MW	CG	N
0.180	4.57	70411S	.50	12.7	.122	3.1	35	6.2	.14	3.5	4.9	22	.26	6.7	0.029	0.7	9.13	SST	CG	N
0.180	4.57	70429	.50	12.7	.116	2.9	65	11	.15	3.8	9.7	43	.29	7.4	0.032	0.8	9.13	MW	CG	N
0.180	4.57	70429S	.50	12.7	.116	2.9	55	9.7	.12	3.0	6.5	29	.29	7.4	0.032	0.8	9.13	SST	CG	N
0.180	4.57	70446	.50	12.7	.110	2.8	99	17	.12	3.1	12	53	.32	8.1	0.035	0.9	9.13	MW	CG	N
0.180	4.57	70446S	.50	12.7	.110	2.8	84	15	.10	2.4	8.0	36	.32	8.1	0.035	0.9	9.13	SST	CG	N
0.180	4.57	B2-34	.55	13.9	.134	3.4	13	2.3	.29	7.5	3.9	18	.22	5.7	0.023	0.6	9.75	MW	CG	N
0.180	4.57	70249	.56	14.2	.156	4.0	1.5	.26	.43	11	.64	2.8	.08	1.9	0.012	0.3	6.25	MW	CG	N
0.180	4.57	70249S	.56	14.2	.156	4.0	1.3	.23	.32	8.0	.41	1.8	.08	1.9	0.012	0.3	6.25	SST	CG	N
0.180	4.57	70264	.56	14.2	.152	3.9	2.5	.43	.41	10	1.0	4.5	.10	2.4	0.014	0.4	6.88	MW	CG	N
0.180	4.57	70264S	.56	14.2	.152	3.9	2.2	.38	.30	7.6	.64	2.9	.10	2.4	0.014	0.4	6.88	SST	CG	N
0.180	4.57	70285	.56	14.2	.148	3.8	3.9	.67	.35	9.0	1.4	6.0	.12	3.0	0.016	0.4	7.50	MW	CG	N
0.180	4.57	70285S	.56	14.2	.148	3.8	3.3	.57	.28	7.0	.90	4.0	.12	3.0	0.016	0.4	7.50	SST	CG	N
0.180	4.57	70306	.56	14.2	.144	3.7	5.9	1.0	.33	8.3	1.9	8.5	.15	3.7	0.018	0.5	8.13	MW	CG	N
0.180	4.57	70306S	.56	14.2	.144	3.7	5.0	.87	.26	6.5	1.3	5.7	.15	3.7	0.018	0.5	8.13	SST	CG	N
0.180	4.57	70327	.56	14.2	.140	3.6	8.4	1.5	.31	7.9	2.6	12	.17	4.4	0.020	0.5	8.63	MW	CG	N
0.180	4.57	70327S	.56	14.2	.140	3.6	7.2	1.3	.24	6.2	1.7	7.7	.17	4.4	0.020	0.5	8.63	SST	CG	N
0.180	4.57	70348	.56	14.2	.136	3.5	12	2.1	.29	7.4	3.5	15	.20	5.1	0.022	0.6	9.13	MW	CG	N
0.180	4.57	70348S	.56	14.2	.136	3.5	10	1.8	.23	5.8	2.3	10	.20	5.1	0.022	0.6	9.13	SST	CG	N
0.180	4.57	70368	.56	14.2	.132	3.4	17	2.9	.27	6.8	4.5	20	.23	5.9	0.024	0.6	9.63	MW	CG	N
0.180	4.57	70368S	.56	14.2	.132	3.4	14	2.5	.21	5.3	3.0	13	.23	5.9	0.024	0.6	9.63	SST	CG	N
0.180	4.57	70391	.56	14.2	.128	3.3	23	4.1	.23	5.8	5.3	24	.25	6.4	0.026	0.7	9.75	MW	CG	N
0.180	4.57	70391S	.56	14.2	.128	3.3	20	3.5	.18	4.6	3.6	16	.25	6.4	0.026	0.7	9.75	SST	CG	N
0.180	4.57	70412	.56	14.2	.122	3.1	37	6.4	.20	5.1	7.3	32	.29	7.5	0.029	0.7	10.1	MW	CG	N
0.180	4.57	70412S	.56	14.2	.122	3.1	31	5.4	.16	4.0	4.9	22	.29	7.5	0.029	0.7	10.1	SST	CG	N
0.180	4.57	70430	.56	14.2	.116	2.9	58	10	.17	4.2	9.7	43	.32	8.1	0.032					



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70431	.63	16.0	.116	2.9	51	9.0	.19	4.8	9.7	43	.36	9.0	0.032	0.8	11.1	MW	CG	N
0.180	4.57	70431S	.63	16.0	.116	2.9	43	7.6	.15	3.8	6.5	29	.36	9.0	0.032	0.8	11.1	SST	CG	N
0.180	4.57	70448	.63	16.0	.110	2.8	77	14	.15	3.9	12	53	.39	9.9	0.035	0.9	11.1	MW	CG	N
0.180	4.57	70448S	.63	16.0	.110	2.8	66	11	.12	3.1	8.0	36	.39	9.9	0.035	0.9	11.1	SST	CG	N
0.180	4.57	70251	.69	17.5	.156	4.0	1.2	.21	.53	14	.64	2.8	.09	2.2	0.012	0.3	7.25	MW	CG	N
0.180	4.57	70251S	.69	17.5	.156	4.0	1.0	.18	.39	9.9	.41	1.8	.09	2.2	0.012	0.3	7.25	SST	CG	N
0.180	4.57	70266	.69	17.5	.152	3.9	2.0	.35	.50	13	1.0	4.5	.11	2.8	0.014	0.4	8.00	MW	CG	N
0.180	4.57	70266S	.69	17.5	.152	3.9	1.8	.31	.37	9.3	.64	2.9	.11	2.8	0.014	0.4	8.00	SST	CG	N
0.180	4.57	70287	.69	17.5	.148	3.8	3.1	.53	.45	11	1.4	6.0	.14	3.7	0.016	0.4	9.00	MW	CG	N
0.180	4.57	70287S	.69	17.5	.148	3.8	2.6	.45	.35	8.8	.90	4.0	.14	3.7	0.016	0.4	9.00	SST	CG	N
0.180	4.57	70308	.69	17.5	.144	3.7	4.6	.80	.42	11	1.9	8.5	.18	4.5	0.018	0.5	9.75	MW	CG	N
0.180	4.57	70308S	.69	17.5	.144	3.7	3.9	.68	.33	8.4	1.3	5.7	.18	4.5	0.018	0.5	9.75	SST	CG	N
0.180	4.57	70329	.69	17.5	.140	3.6	6.7	1.2	.39	10	2.6	12	.21	5.3	0.020	0.5	10.5	MW	CG	N
0.180	4.57	70329S	.69	17.5	.140	3.6	5.7	.99	.31	7.8	1.7	7.7	.21	5.3	0.020	0.5	10.5	SST	CG	N
0.180	4.57	70350	.69	17.5	.136	3.5	9.6	1.7	.36	9.2	3.5	15	.24	6.1	0.022	0.6	11.0	MW	CG	N
0.180	4.57	70350S	.69	17.5	.136	3.5	8.1	1.4	.28	7.2	2.3	10	.24	6.1	0.022	0.6	11.0	SST	CG	N
0.180	4.57	70371	.69	17.5	.132	3.4	13	2.3	.34	8.6	4.5	20	.28	7.0	0.024	0.6	11.5	MW	CG	N
0.180	4.57	70371S	.69	17.5	.132	3.4	11	2.0	.26	6.7	3.0	13	.28	7.0	0.024	0.6	11.5	SST	CG	N
0.180	4.57	70393	.69	17.5	.128	3.3	19	3.3	.28	7.1	5.3	24	.30	7.6	0.026	0.7	11.5	MW	CG	N
0.180	4.57	70393S	.69	17.5	.128	3.3	16	2.8	.22	5.6	3.6	16	.30	7.6	0.026	0.7	11.5	SST	CG	N
0.180	4.57	70414	.69	17.5	.122	3.1	29	5.1	.25	6.3	7.3	32	.35	8.9	0.029	0.7	12.1	MW	CG	N
0.180	4.57	70414S	.69	17.5	.122	3.1	25	4.3	.20	5.0	4.9	22	.35	8.9	0.029	0.7	12.1	SST	CG	N
0.180	4.57	70432	.69	17.5	.116	2.9	47	8.3	.20	5.2	9.7	43	.38	9.7	0.032	0.8	11.9	MW	CG	N
0.180	4.57	70432S	.69	17.5	.116	2.9	40	7.0	.16	4.1	6.5	29	.38	9.7	0.032	0.8	11.9	SST	CG	N
0.180	4.57	70449	.69	17.5	.110	2.8	69	12	.17	4.4	12	53	.43	11.0	0.035	0.9	12.4	MW	CG	N
0.180	4.57	70449S	.69	17.5	.110	2.8	58	10	.14	3.5	8.0	36	.43	11.0	0.035	0.9	12.4	SST	CG	N
0.180	4.57	70252	.75	19.1	.156	4.0	1.1	.19	.58	15	.64	2.8	.09	2.4	0.012	0.3	7.75	MW	CG	N
0.180	4.57	70252S	.75	19.1	.156	4.0	.95	.17	.43	11	.41	1.8	.09	2.4	0.012	0.3	7.75	SST	CG	N
0.180	4.57	70267	.75	19.1	.152	3.9	1.9	.33	.54	14	1.0	4.5	.12	3.0	0.014	0.4	8.50	MW	CG	N
0.180	4.57	70267S	.75	19.1	.152	3.9	1.6	.28	.40	10	.64	2.9	.12	3.0	0.014	0.4	8.50	SST	CG	N
0.180	4.57	70288	.75	19.1	.148	3.8	2.7	.46	.51	13	1.4	6.0	.16	4.1	0.016	0.4	10.0	MW	CG	N
0.180	4.57	70288S	.75	19.1	.148	3.8	2.3	.39	.40	10	.90	4.0	.16	4.1	0.016	0.4	10.0	SST	CG	N
0.180	4.57	70309	.75	19.1	.144	3.7	4.1	.71	.47	12	1.9	8.5	.19	4.9	0.018	0.5	10.8	MW	CG	N
0.180	4.57	70309S	.75	19.1	.144	3.7	3.4	.60	.37	9.4	1.3	5.7	.19	4.9	0.018	0.5	10.8	SST	CG	N
0.180	4.57	70330	.75	19.1	.140	3.6	6.2	1.1	.43	11	2.6	12	.22	5.7	0.020	0.5	11.1	MW	CG	N
0.180	4.57	70330S	.75	19.1	.140	3.6	5.2	.92	.33	8.5	1.7	7.7	.22	5.7	0.020	0.5	11.1	SST	CG	N
0.180	4.57	70351	.75	19.1	.136	3.5	8.6	1.5	.40	10	3.5	15	.26	6.6	0.022	0.6	11.9	MW	CG	N
0.180	4.57	70351S	.75	19.1	.136	3.5	7.3	1.3	.31	8.0	2.3	10	.26	6.6	0.022	0.6	11.9	SST	CG	N
0.180	4.57	70372	.75	19.1	.132	3.4	12	2.1	.37	9.4	4.5	20	.30	7.5	0.024	0.6	12.4	MW	CG	N
0.180	4.57	70372S	.75	19.1	.132	3.4	10	1.8	.29	7.3	3.0	13	.30	7.5	0.024	0.6	12.4	SST	CG	N
0.180	4.57	70394	.75	19.1	.128	3.3	17	3.0	.31	7.9	5.3	24	.33	8.3	0.026	0.7	12.6	MW	CG	N
0.180	4.57	70394S	.75	19.1	.128	3.3	14	2.5	.25	6.3	3.6	16	.33	8.3	0.026	0.7	12.6	SST	CG	N
0.180	4.57	B4-33	.75	19.1	.128	3.3	14	2.5	.25	6.4	3.6	16	.34	8.6	0.026	0.7	13.0	SST	CG	N
0.180	4.57	70415	.75	19.1	.122	3.1	26	4.6	.28	7.0	7.3	32	.38	9.7	0.029	0.7	13.1	MW	CG	N
0.180	4.57	70415S	.75	19.1	.122	3.1	22	3.9	.22	5.5	4.9	22	.38	9.7	0.029	0.7	13.1	SST	CG	N
0.180	4.57	70433	.75	19.1	.116	2.9	41	7.2	.23	6.0	9.7	43	.42	10.8	0.032	0.8	13.3	MW	CG	N
0.180	4.57	70433S	.75	19.1	.116	2.9	35	6.1	.19	4.7	6.5	29	.42	10.8	0.032	0.8	13.3	SST	CG	N
0.180	4.57	70450	.75	19.1	.110	2.8	62	11	.19	4.8	12	53	.47	11.9	0.035	0.9	13.4	MW	CG	N
0.180	4.57	70450S	.75	19.1	.110	2.8	53	9.3	.15	3.8	8.0	36	.47	11.9	0.035	0.9	13.4	SST	CG	N
0.180	4.57	70253	.81	20.6	.156	4.0	1.0	.18	.63	16	.64	2.8	.10	2.5	0.012	0.3	8.25	MW	CG	N
0.180	4.57	70253S	.81	20.6	.156	4.0	.88	.15	.46	12	.41	1.8	.10	2.5	0.012	0.3	8.25	SST	CG	N
0.180	4.57	70269	.81	20.6	.152	3.9	1.7	.30	.60	15	1.0	4.5	.13	3.3	0.014	0.4	9.13	MW	CG	N
0.180	4.57	70269S	.81	20.6	.152	3.9	1.5	.26	.44	11	.64	2.9	.13	3.3	0.014	0.4	9.13	SST	CG	N
0.180	4.57	70290	.81	20.6	.148	3.8	2.6	.46	.52	13	1.4	6.0	.16	4.2	0.016	0.4	10.3	MW	CG	N
0.180	4.57	70290S	.81	20.6	.148	3.8	2.2	.39	.41	10	.90	4.0	.16	4.2	0.016	0.4	10.3	SST	CG	N
0.180	4.57	70311	.81	20.6	.144	3.7	3.9	.68	.49	13	1.9	8.5	.20	5.1	0.018	0.5	11.1	MW	CG	N
0.180	4.57	70311S	.81	20.6	.144	3.7	3.3	.58	.39	9.8	1.3	5.7	.20	5.1	0.018	0.5	11.1	SST	CG	N
0.180	4.57	70332	.81	20.6	.140	3.6	5.6	.98	.47	12	2.6	12	.24	6.1	0.020	0.5	12.0	MW	CG	N



1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70333	.88	22.4	.140	3.6	5.2	.91	.50	13	2.6	12	.26	6.5	0.020	0.5	12.8	MW	CG	N
0.180	4.57	70333S	.88	22.4	.140	3.6	4.4	.77	.39	10	1.7	7.7	.26	6.5	0.020	0.5	12.8	SST	CG	N
0.180	4.57	70354	.88	22.4	.136	3.5	7.4	1.3	.47	12	3.5	15	.30	7.5	0.022	0.6	13.5	MW	CG	N
0.180	4.57	70354S	.88	22.4	.136	3.5	6.3	1.1	.37	9.3	2.3	10	.30	7.5	0.022	0.6	13.5	SST	CG	N
0.180	4.57	70375	.88	22.4	.132	3.4	10	1.8	.43	11	4.5	20	.34	8.7	0.024	0.6	14.3	MW	CG	N
0.180	4.57	70375S	.88	22.4	.132	3.4	8.7	1.5	.34	8.6	3.0	13	.34	8.7	0.024	0.6	14.3	SST	CG	N
0.180	4.57	70396	.88	22.4	.128	3.3	15	2.6	.36	9.2	5.3	24	.37	9.4	0.026	0.7	14.3	MW	CG	N
0.180	4.57	70396S	.88	22.4	.128	3.3	12	2.2	.28	7.2	3.6	16	.37	9.4	0.026	0.7	14.3	SST	CG	N
0.180	4.57	70417	.88	22.4	.122	3.1	22	3.9	.33	8.3	7.3	32	.44	11.1	0.029	0.7	15.1	MW	CG	N
0.180	4.57	70417S	.88	22.4	.122	3.1	19	3.3	.26	6.5	4.9	22	.44	11.1	0.029	0.7	15.1	SST	CG	N
0.180	4.57	70435	.88	22.4	.116	2.9	34	5.9	.29	7.3	9.7	43	.50	12.8	0.032	0.8	15.8	MW	CG	N
0.180	4.57	70435S	.88	22.4	.116	2.9	29	5.0	.23	5.7	6.5	29	.50	12.8	0.032	0.8	15.8	SST	CG	N
0.180	4.57	70453	.88	22.4	.110	2.8	52	9.2	.23	5.8	12	53	.54	13.8	0.035	0.9	15.5	MW	CG	N
0.180	4.57	70453S	.88	22.4	.110	2.8	45	7.8	.18	4.6	8.0	36	.54	13.8	0.035	0.9	15.5	SST	CG	N
0.180	4.57	70255	.94	23.9	.156	4.0	.90	.16	.71	18	.64	2.8	.11	2.7	0.012	0.3	9.00	MW	CG	N
0.180	4.57	70255S	.94	23.9	.156	4.0	.78	.14	.52	13	.41	1.8	.11	2.7	0.012	0.3	9.00	SST	CG	N
0.180	4.57	70272	.94	23.9	.152	3.9	1.5	.26	.67	17	1.0	4.5	.14	3.6	0.014	0.4	10.0	MW	CG	N
0.180	4.57	70272S	.94	23.9	.152	3.9	1.3	.23	.49	12	.64	2.9	.14	3.6	0.014	0.4	10.0	SST	CG	N
0.180	4.57	70293	.94	23.9	.148	3.8	2.3	.40	.59	15	1.4	6.0	.18	4.6	0.016	0.4	11.3	MW	CG	N
0.180	4.57	70293S	.94	23.9	.148	3.8	2.0	.34	.46	12	.90	4.0	.18	4.6	0.016	0.4	11.3	SST	CG	N
0.180	4.57	70314	.94	23.9	.144	3.7	3.4	.60	.57	14	1.9	8.5	.23	5.7	0.018	0.5	12.5	MW	CG	N
0.180	4.57	70314S	.94	23.9	.144	3.7	2.9	.51	.44	11	1.3	5.7	.23	5.7	0.018	0.5	12.5	SST	CG	N
0.180	4.57	70335	.94	23.9	.140	3.6	4.9	.86	.53	14	2.6	12	.27	6.9	0.020	0.5	13.5	MW	CG	N
0.180	4.57	70335S	.94	23.9	.140	3.6	4.2	.73	.42	11	1.7	7.7	.27	6.9	0.020	0.5	13.5	SST	CG	N
0.180	4.57	70355	.94	23.9	.136	3.5	6.8	1.2	.51	13	3.5	15	.32	8.1	0.022	0.6	14.5	MW	CG	N
0.180	4.57	70355S	.94	23.9	.136	3.5	5.8	1.0	.40	10	2.3	10	.32	8.1	0.022	0.6	14.5	SST	CG	N
0.180	4.57	70377	.94	23.9	.132	3.4	9.5	1.7	.47	12	4.5	20	.37	9.3	0.024	0.6	15.3	MW	CG	N
0.180	4.57	70377S	.94	23.9	.132	3.4	8.1	1.4	.37	9.3	3.0	13	.37	9.3	0.024	0.6	15.3	SST	CG	N
0.180	4.57	70398	.94	23.9	.128	3.3	13	2.3	.41	10	5.3	24	.41	10.5	0.026	0.7	15.9	MW	CG	N
0.180	4.57	70398S	.94	23.9	.128	3.3	11	1.9	.32	8.2	3.6	16	.41	10.5	0.026	0.7	15.9	SST	CG	N
0.180	4.57	70418	.94	23.9	.122	3.1	21	3.6	.35	8.9	7.3	32	.47	12.0	0.029	0.7	16.3	MW	CG	N
0.180	4.57	70418S	.94	23.9	.122	3.1	18	3.1	.28	7.0	4.9	22	.47	12.0	0.029	0.7	16.3	SST	CG	N
0.180	4.57	70436	.94	23.9	.116	2.9	32	5.5	.31	7.8	9.7	43	.54	13.6	0.032	0.8	16.8	MW	CG	N
0.180	4.57	70436S	.94	23.9	.116	2.9	27	4.7	.24	6.1	6.5	29	.54	13.6	0.032	0.8	16.8	SST	CG	N
0.180	4.57	70452	.94	23.9	.110	2.8	49	8.5	.24	6.2	12	53	.58	14.7	0.035	0.9	16.5	MW	CG	N
0.180	4.57	70452S	.94	23.9	.110	2.8	41	7.3	.19	4.9	8.0	36	.58	14.7	0.035	0.9	16.5	SST	CG	N
0.180	4.57	70256	1.00	25.4	.156	4.0	.80	.14	.80	20	.64	2.8	.12	3.0	0.012	0.3	9.88	MW	CG	N
0.180	4.57	70256S	1.00	25.4	.156	4.0	.69	.12	.59	15	.41	1.8	.12	3.0	0.012	0.3	9.88	SST	CG	N
0.180	4.57	70273	1.00	25.4	.152	3.9	1.4	.24	.74	19	1.0	4.5	.15	3.9	0.014	0.4	10.9	MW	CG	N
0.180	4.57	70273S	1.00	25.4	.152	3.9	1.2	.20	.56	14	.64	2.9	.15	3.9	0.014	0.4	10.9	SST	CG	N
0.180	4.57	70294	1.00	25.4	.148	3.8	2.1	.36	.66	17	1.4	6.0	.20	5.0	0.016	0.4	12.4	MW	CG	N
0.180	4.57	70294S	1.00	25.4	.148	3.8	1.7	.31	.52	13	.90	4.0	.20	5.0	0.016	0.4	12.4	SST	CG	N
0.180	4.57	70315	1.00	25.4	.144	3.7	3.2	.55	.61	15	1.9	8.5	.24	6.1	0.018	0.5	13.3	MW	CG	N
0.180	4.57	70315S	1.00	25.4	.144	3.7	2.7	.47	.48	12	1.3	5.7	.24	6.1	0.018	0.5	13.3	SST	CG	N
0.180	4.57	70336	1.00	25.4	.140	3.6	4.6	.80	.58	15	2.6	12	.29	7.3	0.020	0.5	14.4	MW	CG	N
0.180	4.57	70336S	1.00	25.4	.140	3.6	3.9	.68	.45	11	1.7	7.7	.29	7.3	0.020	0.5	14.4	SST	CG	N
0.180	4.57	70356	1.00	25.4	.136	3.5	6.4	1.1	.54	14	3.5	15	.34	8.6	0.022	0.6	15.4	MW	CG	N
0.180	4.57	70356S	1.00	25.4	.136	3.5	5.4	.95	.42	11	2.3	10	.34	8.6	0.022	0.6	15.4	SST	CG	N
0.180	4.57	70378	1.00	25.4	.132	3.4	9.0	1.6	.50	13	4.5	20	.38	9.8	0.024	0.6	16.0	MW	CG	N
0.180	4.57	70378S	1.00	25.4	.132	3.4	7.7	1.3	.39	9.9	3.0	13	.38	9.8	0.024	0.6	16.0	SST	CG	N
0.180	4.57	70399	1.00	25.4	.128	3.3	12	2.1	.43	11	5.3	24	.44	11.1	0.026	0.7	16.8	MW	CG	N
0.180	4.57	70399S	1.00	25.4	.128	3.3	10	1.8	.34	8.7	3.6	16	.44	11.1	0.026	0.7	16.8	SST	CG	N
0.180	4.57	70419	1.00	25.4	.122	3.1	19	3.4	.38	9.6	7.3	32	.50	12.8	0.029	0.7	17.4	MW	CG	N
0.180	4.57	70419S	1.00	25.4	.122	3.1	16	2.9	.30	7.6	4.9	22	.50	12.8	0.029	0.7	17.4	SST	CG	N
0.180	4.57	70437	1.00	25.4	.116	2.9	29	5.1	.33	8.4	9.7	43	.57	14.5	0.032	0.8	17.9	MW	CG	N
0.180	4.57	70437S	1.00	25.4	.116	2.9	25	4.3	.26	6.6	6.5	29	.57	14.5	0.032	0.8	17.9	SST	CG	N
0.180	4.57	70454	1.00	25.4	.110	2.8	46	8.0	.26	6.6	12	53	.61	15.6	0.035	0.9	17.5	MW	CG	N
0.180	4.57	70454S	1.00	25.4	.110	2.8	39	6.8	.21	5.2	8.0	36	.61	15.6	0.035	0.9	17.5	SST	CG	N
0.180	4.57	70275	1.13	28.7	.152	3.9	1.2	.21												



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	F NISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70276	1.25	31.8	.152	3.9	1.1	.19	.92	23	1.0	4.5	.18	4.6	0.014	0.4	13.0	MW	CG	N
0.180	4.57	70276S	1.25	31.8	.152	3.9	.94	.16	.69	17	.64	2.9	.18	4.6	0.014	0.4	13.0	SST	CG	N
0.180	4.57	70297	1.25	31.8	.148	3.8	1.6	.28	.85	22	1.4	6.0	.25	6.2	0.016	0.4	15.4	MW	CG	N
0.180	4.57	70297S	1.25	31.8	.148	3.8	1.4	.24	.66	17	.90	4.0	.25	6.2	0.016	0.4	15.4	SST	CG	N
0.180	4.57	70318	1.25	31.8	.144	3.7	2.6	.45	.75	19	1.9	8.5	.29	7.3	0.018	0.5	15.9	MW	CG	N
0.180	4.57	70318S	1.25	31.8	.144	3.7	2.2	.38	.59	15	1.3	5.7	.29	7.3	0.018	0.5	15.9	SST	CG	N
0.180	4.57	70339	1.25	31.8	.140	3.6	3.6	.63	.73	18	2.6	12	.35	9.0	0.020	0.5	17.6	MW	CG	N
0.180	4.57	70339S	1.25	31.8	.140	3.6	3.1	.54	.57	14	1.7	7.7	.35	9.0	0.020	0.5	17.6	SST	CG	N
0.180	4.57	70358	1.25	31.8	.136	3.5	5.1	.89	.68	17	3.5	15	.41	10.5	0.022	0.6	18.8	MW	CG	N
0.180	4.57	70358S	1.25	31.8	.136	3.5	4.3	.76	.53	13	2.3	10	.41	10.5	0.022	0.6	18.8	SST	CG	N
0.180	4.57	70380	1.25	31.8	.132	3.4	7.1	1.2	.63	16	4.5	20	.48	12.1	0.024	0.6	19.9	MW	CG	N
0.180	4.57	70380S	1.25	31.8	.132	3.4	6.0	1.0	.50	13	3.0	13	.48	12.1	0.024	0.6	19.9	SST	CG	N
0.180	4.57	70401	1.25	31.8	.128	3.3	9.7	1.7	.55	14	5.3	24	.53	13.5	0.026	0.7	20.5	MW	CG	N
0.180	4.57	70401S	1.25	31.8	.128	3.3	8.2	1.4	.43	11	3.6	16	.53	13.5	0.026	0.7	20.5	SST	CG	N
0.180	4.57	70421	1.25	31.8	.122	3.1	15	2.7	.48	12	7.3	32	.62	15.7	0.029	0.7	21.4	MW	CG	N
0.180	4.57	70421S	1.25	31.8	.122	3.1	13	2.3	.38	9.6	4.9	22	.62	15.7	0.029	0.7	21.4	SST	CG	N
0.180	4.57	70439	1.25	31.8	.116	2.9	23	4.1	.42	11	9.7	43	.71	18.0	0.032	0.8	22.1	MW	CG	N
0.180	4.57	70439S	1.25	31.8	.116	2.9	20	3.4	.33	8.4	6.5	29	.71	18.0	0.032	0.8	22.1	SST	CG	N
0.180	4.57	70456	1.25	31.8	.110	2.8	36	6.3	.33	8.4	12	53	.76	19.2	0.035	0.9	21.6	MW	CG	N
0.180	4.57	70456S	1.25	31.8	.110	2.8	31	5.4	.26	6.7	8.0	36	.76	19.2	0.035	0.9	21.6	SST	CG	N
0.180	4.57	70277	1.38	35.1	.152	3.9	.98	.17	1.0	26	1.0	4.5	.20	5.1	0.014	0.4	14.4	MW	CG	N
0.180	4.57	70277S	1.38	35.1	.152	3.9	.83	.15	.78	20	.64	2.9	.20	5.1	0.014	0.4	14.4	SST	CG	N
0.180	4.57	70298	1.38	35.1	.148	3.8	1.5	.25	.94	24	1.4	6.0	.27	6.8	0.016	0.4	16.8	MW	CG	N
0.180	4.57	70298S	1.38	35.1	.148	3.8	1.2	.22	.73	19	.90	4.0	.27	6.8	0.016	0.4	16.8	SST	CG	N
0.180	4.57	70319	1.38	35.1	.144	3.7	2.3	.40	.84	21	1.9	8.5	.32	8.1	0.018	0.5	17.6	MW	CG	N
0.180	4.57	70319S	1.38	35.1	.144	3.7	1.9	.34	.66	17	1.3	5.7	.32	8.1	0.018	0.5	17.6	SST	CG	N
0.180	4.57	70340	1.38	35.1	.140	3.6	3.3	.57	.81	20	2.6	12	.39	9.8	0.020	0.5	19.3	MW	CG	N
0.180	4.57	70340S	1.38	35.1	.140	3.6	2.8	.48	.63	16	1.7	7.7	.39	9.8	0.020	0.5	19.3	SST	CG	N
0.180	4.57	70360	1.38	35.1	.136	3.5	4.6	.81	.75	19	3.5	15	.45	11.5	0.022	0.6	20.5	MW	CG	N
0.180	4.57	70360S	1.38	35.1	.136	3.5	3.9	.68	.59	15	2.3	10	.45	11.5	0.022	0.6	20.5	SST	CG	N
0.180	4.57	70382	1.38	35.1	.132	3.4	6.4	1.1	.70	18	4.5	20	.52	13.2	0.024	0.6	21.6	MW	CG	N
0.180	4.57	70382S	1.38	35.1	.132	3.4	5.4	.95	.55	14	3.0	13	.52	13.2	0.024	0.6	21.6	SST	CG	N
0.180	4.57	70403	1.38	35.1	.128	3.3	8.7	1.5	.61	16	5.3	24	.59	14.9	0.026	0.7	22.6	MW	CG	N
0.180	4.57	70403S	1.38	35.1	.128	3.3	7.4	1.3	.48	12	3.6	16	.59	14.9	0.026	0.7	22.6	SST	CG	N
0.180	4.57	70422	1.38	35.1	.122	3.1	14	2.4	.53	13	7.3	32	.68	17.3	0.029	0.7	23.5	MW	CG	N
0.180	4.57	70422S	1.38	35.1	.122	3.1	12	2.0	.42	11	4.9	22	.68	17.3	0.029	0.7	23.5	SST	CG	N
0.180	4.57	70440	1.38	35.1	.116	2.9	21	3.6	.46	12	9.7	43	.78	19.8	0.032	0.8	24.4	MW	CG	N
0.180	4.57	70440S	1.38	35.1	.116	2.9	18	3.1	.37	9.3	6.5	29	.78	19.8	0.032	0.8	24.4	SST	CG	N
0.180	4.57	70258	1.50	38.1	.156	4.0	.60	.10	1.1	27	.64	2.8	.15	3.8	0.012	0.3	12.5	MW	CG	N
0.180	4.57	70258S	1.50	38.1	.156	4.0	.52	.09	.78	20	.41	1.8	.15	3.8	0.012	0.3	12.5	SST	CG	N
0.180	4.57	70278	1.50	38.1	.152	3.9	.89	.15	1.1	29	1.0	4.5	.22	5.6	0.014	0.4	15.6	MW	CG	N
0.180	4.57	70278S	1.50	38.1	.152	3.9	.75	.13	.85	22	.64	2.9	.22	5.6	0.014	0.4	15.6	SST	CG	N
0.180	4.57	70299	1.50	38.1	.148	3.8	1.3	.23	1.0	27	1.4	6.0	.29	7.5	0.016	0.4	18.4	MW	CG	N
0.180	4.57	70299S	1.50	38.1	.148	3.8	1.1	.19	.82	21	.90	4.0	.29	7.5	0.016	0.4	18.4	SST	CG	N
0.180	4.57	70320	1.50	38.1	.144	3.7	2.1	.36	.94	24	1.9	8.5	.35	8.9	0.018	0.5	19.4	MW	CG	N
0.180	4.57	70320S	1.50	38.1	.144	3.7	1.7	.31	.73	19	1.3	5.7	.35	8.9	0.018	0.5	19.4	SST	CG	N
0.180	4.57	70341	1.50	38.1	.140	3.6	3.0	.52	.89	23	2.6	12	.42	10.7	0.020	0.5	21.0	MW	CG	N
0.180	4.57	70341S	1.50	38.1	.140	3.6	2.5	.44	.69	18	1.7	7.7	.42	10.7	0.020	0.5	21.0	SST	CG	N
0.180	4.57	70361	1.50	38.1	.136	3.5	4.2	.74	.82	21	3.5	15	.49	12.5	0.022	0.6	22.4	MW	CG	N
0.180	4.57	70361S	1.50	38.1	.136	3.5	3.6	.63	.64	16	2.3	10	.49	12.5	0.022	0.6	22.4	SST	CG	N
0.180	4.57	70383	1.50	38.1	.132	3.4	5.8	1.0	.77	19	4.5	20	.57	14.4	0.024	0.6	23.6	MW	CG	N
0.180	4.57	70383S	1.50	38.1	.132	3.4	5.0	.87	.60	15	3.0	13	.57	14.4	0.024	0.6	23.6	SST	CG	N
0.180	4.57	70404	1.50	38.1	.128	3.3	8.0	1.4	.66	17	5.3	24	.64	16.2	0.026	0.7	24.5	MW	CG	N
0.180	4.57	70404S	1.50	38.1	.128	3.3	6.8	1.2	.52	13	3.6	16	.64	16.2	0.026	0.7	24.5	SST	CG	N
0.180	4.57	70423	1.50	38.1	.122	3.1	13	2.2	.58	15	7.3	32	.74	18.8	0.029	0.7	25.5	MW	CG	N
0.180	4.57	70423S	1.50	38.1	.122	3.1	11	1.9	.46	12	4.9	22	.74	18.8	0.029	0.7	25.5	SST	CG	N
0.180	4.57	70441	1.50	38.1	.116	2.9	19	3.4	.50	13	9.7	43	.84	21.3	0.032	0.8	26.3	MW	CG	N
0.180	4.57	70441S	1.50	38																



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.180	4.57	70406	2.00	50.8	.128	3.3	6.0	1.0	.89	23	5.3	24	.84	21.3	0.026	0.7	32.3	MW	CG	N
0.180	4.57	70406S	2.00	50.8	.128	3.3	5.1	.89	.70	18	3.6	16	.84	21.3	0.026	0.7	32.3	SST	CG	N
0.180	4.57	70425	2.00	50.8	.122	3.1	9.4	1.6	.78	20	7.3	32	.98	24.8	0.029	0.7	33.6	MW	CG	N
0.180	4.57	70425S	2.00	50.8	.122	3.1	7.9	1.4	.61	16	4.9	22	.98	24.8	0.029	0.7	33.6	SST	CG	N
0.180	4.57	70443	2.00	50.8	.116	2.9	14	2.5	.69	17	9.7	43	1.12	28.4	0.032	0.8	35.0	MW	CG	N
0.180	4.57	70443S	2.00	50.8	.116	2.9	12	2.1	.54	14	6.5	29	1.12	28.4	0.032	0.8	35.0	SST	CG	N
0.180	4.57	70459	2.00	50.8	.110	2.8	22	3.9	.54	14	12	53	1.19	30.3	0.035	0.9	34.1	MW	CG	N
0.180	4.57	70459S	2.00	50.8	.110	2.8	19	3.3	.43	11	8.0	36	1.19	30.3	0.035	0.9	34.1	SST	CG	N
0.184	4.67	12764	.25	6.4	.164	4.2	.78	.14	.19	4.7	.14	.64	.07	1.7	0.010	0.3	5.50	MW	CG	N
0.184	4.67	B4-24	.86	21.8	.138	3.5	7.4	1.3	.51	13	3.8	17	.35	8.8	0.023	0.6	15.0	MW	CG	BO
0.188	4.78	00-60	.19	4.8	.160	4.1	11	1.9	.09	2.3	.97	4.3	.06	1.4	0.014	0.4	3.00	MW	C	N
0.188	4.78	AA-33	.19	4.8	.156	4.0	8.4	1.5	.10	2.6	.87	3.9	.08	2.0	0.016	0.4	4.00	SST	C	N
0.188	4.78	CC-5	.19	4.8	.140	3.6	110	19	.04	.99	4.3	19	.10	2.4	0.024	0.6	3.00	MW	C	N
0.188	4.78	V-75	.19	4.8	.140	3.6	64	11	.04	1.1	2.9	13	.11	2.7	0.024	0.6	3.50	SST	C	N
0.188	4.78	U-15	.19	4.8	.130	3.3	258	45	.03	.69	7.0	31	.12	2.9	0.029	0.7	3.00	MW	C	Z
0.188	4.78	PP-69	.22	5.6	.148	3.8	15	2.6	.10	2.5	1.4	6.4	.12	3.0	0.020	0.5	5.00	SST	C	N
0.188	4.78	B1-22	.23	5.9	.138	3.5	38	6.6	.08	2.1	3.1	14	.15	3.8	0.025	0.6	5.00	SST	C	N
0.188	4.78	FF-62	.25	6.4	.158	4.0	7.2	1.3	.15	3.8	1.1	4.8	.08	1.9	0.015	0.4	4.00	MW	C	N
0.188	4.78	S-1460	.25	6.4	.158	4.0	4.5	.79	.16	4.0	.72	3.2	.09	2.2	0.015	0.4	4.75	SST	C	N
0.188	4.78	B9-31	.25	6.4	.150	3.8	16	2.7	.14	3.5	2.2	9.6	.09	2.2	0.019	0.5	4.50	MW	CG	Z
0.188	4.78	LL-15	.25	6.4	.148	3.8	22	3.8	.08	2.0	1.7	7.4	.10	2.5	0.020	0.5	4.00	SST	C	N
0.188	4.78	II-2	.25	6.4	.144	3.7	26	4.6	.08	2.2	2.2	9.8	.12	3.1	0.022	0.6	4.50	SST	C	N
0.188	4.78	A10-6	.25	6.4	.142	3.6	30	5.3	.12	3.2	3.8	17	.12	2.9	0.023	0.6	5.00	MW	CG	GI
0.188	4.78	S-1280	.25	6.4	.138	3.5	33	5.7	.09	2.4	3.1	14	.14	3.5	0.025	0.6	5.50	SST	CG	N
0.188	4.78	EE-3	.25	6.4	.136	3.5	52	9.2	.09	2.4	4.9	22	.16	4.0	0.026	0.7	5.00	MW	C	N
0.188	4.78	O-13	.25	6.4	.136	3.5	63	11	.08	2.1	5.1	23	.14	3.6	0.026	0.7	4.50	MW	C	N
0.188	4.78	V-83	.25	6.4	.136	3.5	155	27	.03	.84	5.1	23	.10	2.6	0.026	0.7	3.00	MW	C	N
0.188	4.78	A-44	.25	6.4	.132	3.4	64	11	.07	1.7	4.2	19	.14	3.6	0.028	0.7	5.00	SST	CG	N
0.188	4.78	AA-2	.25	6.4	.104	2.6	639	112	.02	.55	14	61	.19	4.7	0.042	1.1	4.25	SPR	CG	N
0.188	4.78	G-60	.28	7.1	.154	3.9	5.3	.93	.16	4.1	.86	3.8	.12	3.0	0.017	0.4	6.00	SST	C	N
0.188	4.78	O-119	.28	7.1	.154	3.9	8.1	1.4	.18	4.6	1.5	6.5	.10	2.6	0.017	0.4	5.00	MW	C	N
0.188	4.78	EE-11	.28	7.1	.142	3.6	13	2.3	.10	2.5	1.3	5.7	.18	4.7	0.023	0.6	8.00	SST	CG	N
0.188	4.78	F-18	.28	7.1	.138	3.5	38	6.6	.12	3.0	4.5	20	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.188	4.78	908	.31	7.9	.170	4.3	.37	.07	.24	6.2	.09	.40	.07	1.7	0.009	0.2	6.50	MW	C	Z
0.188	4.78	FF-7	.31	7.9	.170	4.3	.35	.06	.24	6.2	.09	.38	.07	1.8	0.009	0.2	6.75	MW	C	N
0.188	4.78	A9-2	.31	7.9	.164	4.2	1.2	.20	.23	5.7	.26	1.2	.09	2.2	0.012	0.3	6.25	SST	C	N
0.188	4.78	10063	.31	7.9	.158	4.0	2.9	.50	.19	4.9	.55	2.4	.12	3.0	0.015	0.4	7.00	MW	C	GI
0.188	4.78	V-14	.31	7.9	.158	4.0	1.6	.27	.15	3.7	.23	1.0	.17	4.2	0.015	0.4	10.0	SST	C	N
0.188	4.78	G-70	.31	7.9	.158	4.0	3.5	.62	.21	5.3	.73	3.2	.11	2.7	0.015	0.4	6.00	MW	C	N
0.188	4.78	F-76	.31	7.9	.156	4.0	5.5	.96	.16	4.0	.87	3.9	.08	2.0	0.016	0.4	5.00	SST	CG	N
0.188	4.78	DD-70	.31	7.9	.152	3.9	8.4	1.5	.15	3.7	1.2	5.5	.11	2.9	0.018	0.5	5.25	SST	C	N
0.188	4.78	S-1007	.31	7.9	.152	3.9	11	1.9	.11	2.9	1.2	5.5	.10	2.5	0.018	0.5	4.50	SST	C	N
0.188	4.78	M-119	.31	7.9	.150	3.8	17	3.0	.08	2.1	1.4	6.4	.10	2.4	0.019	0.5	4.00	SST	C	N
0.188	4.78	2983	.31	7.9	.148	3.8	20	3.5	.13	3.2	2.5	11	.11	2.8	0.020	0.5	4.50	MW	C	Z
0.188	4.78	II-49	.31	7.9	.148	3.8	9.9	1.7	.17	4.4	1.7	7.6	.14	3.6	0.020	0.5	7.00	MW	CG	Z
0.188	4.78	DD-12	.31	7.9	.144	3.7	22	3.8	.10	2.6	2.2	9.8	.13	3.4	0.022	0.6	5.00	SST	C	N
0.188	4.78	J-96	.31	7.9	.144	3.7	18	3.2	.18	4.6	3.3	15	.13	3.4	0.022	0.6	6.00	MW	CG	GI
0.188	4.78	2522	.31	7.9	.128	3.3	118	21	.07	1.7	7.7	34	.17	4.2	0.030	0.8	4.50	MW	C	Z
0.188	4.78	A15-7	.31	7.9	.122	3.1	117	20	.06	1.6	7.3	33	.20	5.0	0.033	0.8	6.00	SPR	CG	N
0.188	4.78	A9-22	.34	8.7	.166	4.2	.86	.15	.27	6.8	.23	1.0	.08	2.0	0.011	0.3	6.00	SST	C	N
0.188	4.78	S-853	.34	8.7	.156	4.0	3.6	.64	.22	5.7	.81	3.6	.12	3.0	0.016	0.4	6.50	SST	C	N
0.188	4.78	S-1003	.34	8.7	.152	3.9	6.4	1.1	.19	4.9	1.2	5.5	.13	3.3	0.018	0.5	6.25	SST	C	N
0.188	4.78	F-66	.34	8.7	.136	3.5	39	6.8	.13	3.4	5.1	23	.18	4.6	0.026	0.7	6.00	MW	C	Z
0.188	4.78	F-16	.34	8.7	.122	3.1	114	20	.06	1.6	7.3	33	.23	5.9	0.033	0.8	6.00	HD	C	Z
0.188	4.78	II-86	.38	9.5	.172	4.4	.14	.02	.30	7.6	.04	.18	.08	1.9	0.008	0.2	8.50	SST	C	N
0.188	4.78	VW-13	.38	9.5	.168	4.3	.75	.13	.30	7.7	.23	1.0	.06	1.5	0.010	0.3	5.00	SST	C	N
0.188	4.78	PP-98	.38	9.5	.164	4.2	1.1	.19	.28	7.1	.31	1.4	.10	2.4	0.012	0.3	7.00	MW	C	N
0.188	4.78	II-14	.38	9.5	.156	4.0	4.7	.82	.26	6.7	1.2	5.5	.11	2.8	0.016	0.4	6.00	MW	C	N
0.188	4.78	B12-17	.38	9.5	.152	3.9	8.2	1.4	.23	5.7	1.8	8.2	.10	2.6	0.018	0.5	5.75	MW	CG	N
0.188	4.78	J-39	.38	9.5	.150	3.8	8.8	1.5	.25	6.3	2.2	9.6	.12							



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	J-33	.41	10.3	.144	3.7	10	1.8	.20	5.0	2.0	8.8	.21	5.3	0.022	0.6	8.50	SST	C	N
0.188	4.78	L-49	.41	10.3	.142	3.6	21	3.8	.18	4.5	3.8	17	.17	4.2	0.023	0.6	6.25	MW	C	N
0.188	4.78	J-20	.41	10.3	.138	3.5	44	7.7	.10	2.6	4.6	20	.15	3.8	0.025	0.6	5.00	MW	C	Z
0.188	4.78	Z-86	.41	10.3	.136	3.5	27	4.8	.12	3.2	3.4	15	.18	4.6	0.026	0.7	7.00	SST	CG	N
0.188	4.78	GG-14	.41	10.3	.134	3.4	57	10	.10	2.5	5.7	25	.14	3.6	0.027	0.7	5.25	MW	CG	N
0.188	4.78	J-83	.41	10.3	.134	3.4	31	5.4	.18	4.7	5.7	25	.22	5.5	0.027	0.7	8.00	MW	CG	N
0.188	4.78	F-4	.41	10.3	.134	3.4	37	6.4	.16	4.0	5.7	25	.22	5.5	0.027	0.7	7.00	MW	C	Z
0.188	4.78	JJ-29	.41	10.3	.132	3.4	34	5.9	.13	3.2	4.2	19	.22	5.5	0.028	0.7	7.75	SST	CG	N
0.188	4.78	11108	.41	10.3	.126	3.2	47	8.2	.12	3.1	5.7	25	.26	6.7	0.031	0.8	8.50	SST	CG	N
0.188	4.78	F-68	.41	10.3	.124	3.1	81	14	.08	2.1	6.7	30	.26	6.5	0.032	0.8	7.00	SPR	C	Z
0.188	4.78	3449	.41	10.3	.112	2.8	139	24	.07	1.9	10	46	.32	8.2	0.038	1.0	8.50	SPR	CG	GI
0.188	4.78	S-1427	.44	11.1	.166	4.2	.84	.15	.36	9.1	.30	1.3	.08	2.0	0.011	0.3	6.00	SST	C	N
0.188	4.78	10679	.44	11.1	.164	4.2	.81	.14	.33	8.4	.27	1.2	.11	2.7	0.012	0.3	8.03	SST	C	N
0.188	4.78	10590	.44	11.1	.162	4.1	1.5	.27	.33	8.5	.51	2.3	.10	2.6	0.013	0.3	7.00	MW	C	N
0.188	4.78	M-8	.44	11.1	.152	3.9	6.1	1.1	.29	7.5	1.8	8.0	.14	3.7	0.018	0.5	7.00	MW	C	N
0.188	4.78	W-60A	.44	11.1	.152	3.9	4.9	.87	.25	6.3	1.2	5.5	.15	3.9	0.018	0.5	7.50	SST	C	N
0.188	4.78	4329	.44	11.1	.140	3.6	13	2.2	.16	4.0	2.0	8.7	.28	7.2	0.024	0.6	10.8	MW	C	N
0.188	4.78	A9-9	.44	11.1	.138	3.5	19	3.3	.16	4.1	3.1	14	.21	5.2	0.025	0.6	8.25	SST	CG	N
0.188	4.78	F-98	.44	11.1	.138	3.5	22	3.9	.21	5.3	4.6	20	.23	5.7	0.025	0.6	8.00	MW	C	Z
0.188	4.78	S-1432	.44	11.1	.130	3.3	50	8.7	.09	2.4	4.7	21	.22	5.5	0.029	0.7	6.50	SST	C	N
0.188	4.78	FF-2	.44	11.1	.128	3.3	42	7.4	.17	4.3	7.1	32	.27	6.9	0.030	0.8	9.00	MW	CG	Z
0.188	4.78	F-71	.44	11.1	.124	3.1	62	11	.11	2.7	6.7	30	.30	7.7	0.032	0.8	8.50	SPR	C	Z
0.188	4.78	Z-12	.44	11.1	.124	3.1	64	11	.10	2.5	6.2	28	.27	6.9	0.032	0.8	7.50	SST	C	N
0.188	4.78	S-1512	.47	11.9	.164	4.2	1.1	.20	.34	8.7	.39	1.7	.09	2.2	0.012	0.3	6.25	SST	C	N
0.188	4.78	2553	.47	11.9	.148	3.8	11	1.9	.23	5.9	2.5	11	.15	3.8	0.020	0.5	6.50	MW	C	Z
0.188	4.78	MM-26	.47	11.9	.148	3.8	9.7	1.7	.26	6.6	2.5	11	.16	4.1	0.020	0.5	7.00	MW	C	N
0.188	4.78	Y-77	.47	11.9	.140	3.6	22	3.9	.19	4.9	4.3	19	.19	4.9	0.024	0.6	7.00	MW	C	Z
0.188	4.78	J-78	.47	11.9	.138	3.5	26	4.6	.17	4.4	4.6	20	.20	5.1	0.025	0.6	7.00	MW	C	Z
0.188	4.78	Q-22	.47	11.9	.136	3.5	26	4.6	.19	4.9	5.1	23	.23	5.9	0.026	0.7	8.00	MW	C	Z
0.188	4.78	GG-3	.47	11.9	.130	3.3	51	8.9	.09	2.3	4.7	21	.19	4.8	0.029	0.7	6.50	SST	CG	N
0.188	4.78	FF-59	.47	11.9	.126	3.2	55	9.7	.10	2.6	5.7	25	.26	6.7	0.031	0.8	7.50	SST	C	N
0.188	4.78	II-63	.47	11.9	.118	3.0	102	18	.08	2.1	8.3	37	.28	7.1	0.035	0.9	8.00	SPR	CG	N
0.188	4.78	M-125	.47	11.9	.112	2.8	178	31	.06	1.5	10	46	.30	7.7	0.038	1.0	7.00	SPR	C	N
0.188	4.78	A14-5	.50	12.7	.168	4.3	.26	.04	.38	9.7	.10	.43	.12	3.0	0.010	0.3	11.0	SST	C	N
0.188	4.78	11355	.50	12.7	.164	4.2	1.3	.23	.30	7.7	.39	1.7	.08	2.1	0.012	0.3	5.75	SST	C	N
0.188	4.78	GG-18	.50	12.7	.160	4.1	.93	.16	.32	8.1	.29	1.3	.18	4.6	0.014	0.4	12.0	SST	C	N
0.188	4.78	B5-11	.50	12.7	.158	4.0	2.8	.49	.38	9.7	1.1	4.8	.12	3.0	0.015	0.4	7.00	MW	C	N
0.188	4.78	3727	.50	12.7	.154	3.9	2.3	.41	.27	6.9	.63	2.8	.23	5.8	0.017	0.4	12.5	MW	C	Z
0.188	4.78	CC-61	.50	12.7	.148	3.8	8.2	1.4	.31	7.8	2.5	11	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.188	4.78	K-13	.50	12.7	.148	3.8	6.2	1.1	.28	7.1	1.7	7.7	.22	5.6	0.020	0.5	10.0	MW	C	Z
0.188	4.78	B4-18	.50	12.7	.148	3.8	8.1	1.4	.31	7.9	2.5	11	.18	4.6	0.020	0.5	8.00	MW	C	N
0.188	4.78	NN-29	.50	12.7	.146	3.7	9.0	1.6	.21	5.4	1.9	8.6	.19	4.8	0.021	0.5	8.00	SST	C	N
0.188	4.78	3530	.50	12.7	.144	3.7	8.3	1.5	.26	6.6	2.1	9.6	.24	6.1	0.022	0.6	11.0	MW	CG	Z
0.188	4.78	A13-1	.50	12.7	.144	3.7	12	2.1	.28	7.0	3.3	15	.18	4.6	0.022	0.6	8.25	MW	CG	GI
0.188	4.78	920	.50	12.7	.142	3.6	11	2.0	.25	6.3	2.8	13	.25	6.4	0.023	0.6	10.0	MW	C	Z
0.188	4.78	FF-27	.50	12.7	.140	3.6	28	4.8	.10	2.6	2.9	13	.17	4.3	0.024	0.6	6.00	SST	C	N
0.188	4.78	O-108	.50	12.7	.140	3.6	22	3.9	.19	4.9	4.3	19	.19	4.9	0.024	0.6	7.00	MW	C	BO
0.188	4.78	VV-69	.50	12.7	.140	3.6	16	2.8	.18	4.5	2.9	13	.22	5.5	0.024	0.6	8.00	SST	C	N
0.188	4.78	3986	.50	12.7	.138	3.5	26	4.6	.17	4.4	4.6	20	.20	5.1	0.025	0.6	7.00	MW	C	Z
0.188	4.78	LL-42	.50	12.7	.138	3.5	20	3.6	.22	5.7	4.6	20	.24	6.0	0.025	0.6	8.50	MW	C	N
0.188	4.78	B7-18	.50	12.7	.138	3.4	19	3.4	.24	6.0	4.6	20	.22	5.6	0.025	0.6	8.75	MW	CG	N
0.188	4.78	W-69	.50	12.7	.134	3.4	18.04	3.1	.16	4.1	2.9	12.8	.297	7.4	0.027	0.69	11.0	SST	CG	N
0.188	4.78	528	.50	12.7	.132	3.4	34	5.9	.19	4.8	6.3	28	.27	6.8	0.028	0.7	8.50	MW	C	Z
0.188	4.78	DD-9	.50	12.7	.128	3.3	37	6.5	.14	3.5	5.2	23	.30	7.6	0.030	0.8	9.00	SST	C	N
0.188	4.78	EE-29	.50	12.7	.128	3.3	30	5.3	.14	3.6	4.2	19	.36	9.1	0.030	0.8	12.0	MW	CG	N
0.188	4.78	NN-3	.50	12.7	.128	3.3	42	7.4	.18	4.7	7.7	34	.30	7.6	0.030	0.8	9.00	MW	C	N
0.188	4.78	B6-15	.50	12.7	.126	3.2	47	8.3	.18	4.6	8.5	38	.29	7.3	0.031	0.8	9.25	MW	CG	N
0.188	4.78	PP-82	.50	12.7	.124	3.1	44	7.7	.14	3.6	6.2	28	.35	8.9	0.032	0.8	10.0	SST	C	N
0.188	4.78	S-709	.50	12.7	.124	3.1	50	8												



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FNSH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	II-3	.56	14.3	.130	3.3	52	9.0	.14	3.5	7.0	31	.23	5.9	0.029	0.7	7.00	MW	C	Z
0.188	4.78	Z-91	.56	14.3	.128	3.3	50	8.8	.15	3.9	7.7	34	.27	6.9	0.030	0.8	8.00	MW	C	Z
0.188	4.78	N-25	.56	14.3	.118	3.0	91	16	.09	2.2	7.7	34	.28	7.1	0.035	0.9	8.00	SST	CG	N
0.188	4.78	JJ-18	.59	15.1	.160	4.1	1.1	.19	.41	10	.44	1.9	.18	4.6	0.014	0.4	12.0	MW	C	N
0.188	4.78	U-100	.59	15.1	.160	4.1	1.7	.31	.48	12	.84	3.7	.11	2.8	0.014	0.4	8.00	MW	CG	N
0.188	4.78	O-36	.59	15.1	.152	3.9	6.1	1.1	.30	7.6	1.8	8.2	.14	3.7	0.018	0.5	7.00	MW	C	N
0.188	4.78	A9-15	.59	15.1	.148	3.8	3.1	.55	.27	6.9	.85	3.8	.32	8.1	0.020	0.5	16.0	SST	CG	N
0.188	4.78	Z-46	.59	15.1	.148	3.8	4.8	.84	.35	8.9	1.7	7.4	.22	5.6	0.020	0.5	11.0	SST	CG	N
0.188	4.78	B14-43	.59	15.1	.146	3.7	6.0	1.1	.34	8.7	2.0	9.1	.25	6.4	0.021	0.5	12.0	MW	CG	N
0.188	4.78	B14-48	.59	15.1	.132	3.4	22	3.8	.26	6.5	5.5	25	.34	8.5	0.028	0.7	12.0	MW	CG	N
0.188	4.78	V-50	.59	15.1	.130	3.3	18	3.2	.17	4.4	3.2	14	.42	10.7	0.029	0.7	14.5	SST	CG	N
0.188	4.78	B1-9	.59	15.1	.122	3.1	44	7.6	.16	4.0	6.8	30	.38	9.6	0.033	0.8	11.5	SST	CG	N
0.188	4.78	F-73	.59	15.1	.122	3.1	54	9.4	.14	3.5	7.3	33	.38	9.6	0.033	0.8	10.5	HD	C	N
0.188	4.78	B15-6	.59	15.1	.114	2.9	87	15	.11	2.8	9.7	43	.41	10.3	0.037	0.9	11.0	SPR	CG	N
0.188	4.78	B4-5	.59	15.1	.138	3.5	16	2.8	.29	7.4	4.6	20	.28	7.1	0.025	0.6	10.3	MW	C	N
0.188	4.78	10896	.63	15.9	.170	4.3	.16	.03	.52	13	.08	.37	.11	2.7	0.009	0.2	11.0	SST	C	N
0.188	4.78	RR-13	.63	15.9	.164	4.2	.54	.09	.48	12	.26	1.1	.14	3.7	0.012	0.3	11.0	SST	C	N
0.188	4.78	N-314	.63	15.9	.158	4.0	1.8	.31	.47	12	.83	3.7	.15	3.9	0.015	0.4	10.1	MW	CG	N
0.188	4.78	00-11	.63	15.9	.156	4.0	.86	.15	.27	6.9	.24	1.0	.35	8.9	0.016	0.4	21.0	SST	C	N
0.188	4.78	B9-63	.63	15.9	.150	3.8	6.5	1.1	.33	8.5	2.2	9.6	.15	3.9	0.019	0.5	8.00	MW	CG	N
0.188	4.78	PP-19	.63	15.9	.144	3.7	6.2	1.1	.30	7.5	1.8	8.2	.33	8.4	0.022	0.6	14.0	MW	C	N
0.188	4.78	S-707	.63	15.9	.144	3.7	8.1	1.4	.27	6.9	2.2	9.8	.24	6.1	0.022	0.6	10.0	SST	C	N
0.188	4.78	921	.63	15.9	.142	3.6	13	2.2	.30	7.7	3.8	17	.24	6.0	0.023	0.6	9.25	MW	C	Z
0.188	4.78	A-83	.63	15.9	.138	3.5	11	2.0	.27	6.8	3.1	14	.33	8.3	0.025	0.6	12.0	SST	C	N
0.188	4.78	F-19	.63	15.9	.138	3.5	12	2.1	.28	7.0	3.3	15	.35	8.9	0.025	0.6	13.0	MW	C	Z
0.188	4.78	Q-71	.63	15.9	.136	3.5	14	2.5	.26	6.6	3.7	17	.36	9.2	0.026	0.7	13.0	MW	C	N
0.188	4.78	AA-67	.63	15.9	.128	3.3	33	5.7	.24	6.0	7.7	34	.36	9.1	0.030	0.8	11.0	MW	C	Z
0.188	4.78	NN-84	.63	15.9	.124	3.1	54	9.5	.12	3.2	6.7	30	.30	7.7	0.032	0.8	9.50	SPR	CG	N
0.188	4.78	S-710	.63	15.9	.124	3.1	38	6.7	.16	4.2	6.2	28	.39	10.0	0.032	0.8	11.3	SST	C	N
0.188	4.78	10604	.63	15.9	.122	3.1	51	8.9	.14	3.7	7.3	33	.40	10.1	0.033	0.8	11.0	SPR	C	Z
0.188	4.78	A9-18	.66	16.7	.168	4.3	.24	.04	.53	13	.13	.57	.13	3.2	0.010	0.3	11.5	SST	C	N
0.188	4.78	PP-35	.66	16.7	.152	3.9	3.4	.60	.36	9.2	1.2	5.5	.20	5.0	0.018	0.5	10.0	SST	C	N
0.188	4.78	H-15	.66	16.7	.148	3.8	8.1	1.4	.31	7.9	2.5	11	.18	4.6	0.020	0.5	8.00	MW	C	N
0.188	4.78	G-9	.66	16.7	.140	3.6	13	2.3	.33	8.4	4.3	19	.25	6.4	0.024	0.6	10.5	MW	CG	N
0.188	4.78	F-69	.66	16.7	.136	3.5	18	3.1	.29	7.3	5.1	23	.31	7.8	0.026	0.7	10.8	MW	C	Z
0.188	4.78	Q-18	.69	17.4	.160	4.1	.53	.09	.39	10	.21	.92	.29	7.5	0.014	0.4	20.0	SST	C	N
0.188	4.78	YY-45	.69	17.4	.158	4.0	1.6	.28	.51	13	.81	3.6	.18	4.6	0.015	0.4	11.0	MW	C	N
0.188	4.78	B5-23	.69	17.4	.154	3.9	2.6	.46	.40	10	1.0	4.6	.17	4.3	0.017	0.4	10.0	SST	CG	N
0.188	4.78	A9-47	.69	17.4	.152	3.9	3.9	.68	.47	12	1.8	8.2	.20	5.0	0.018	0.5	10.0	MW	C	BO
0.188	4.78	O-149	.69	17.4	.150	3.8	4.9	.85	.45	11	2.2	9.6	.19	4.8	0.019	0.5	10.0	MW	CG	N
0.188	4.78	I-68	.69	17.4	.148	3.8	3.8	.67	.39	10	1.5	6.6	.30	7.5	0.020	0.5	14.8	MW	CG	N
0.188	4.78	II-30	.69	17.4	.148	3.8	4.9	.85	.43	11	2.1	9.2	.26	6.6	0.020	0.5	12.0	MW	C	N
0.188	4.78	G-76	.69	17.4	.142	3.6	10	1.7	.38	9.7	3.8	17	.25	6.4	0.023	0.6	11.0	MW	CG	N
0.188	4.78	PP-15	.69	17.4	.138	3.5	22	3.9	.21	5.3	4.6	20	.23	5.7	0.025	0.6	8.00	MW	C	BO
0.188	4.78	A14-13	.69	17.4	.132	3.4	23	3.9	.28	7.1	6.3	28	.33	8.4	0.028	0.7	11.8	MW	CG	GI
0.188	4.78	B9-36	.69	17.4	.130	3.3	27	4.7	.26	6.6	7.0	31	.33	8.3	0.029	0.7	11.3	MW	CG	N
0.188	4.78	2610	.69	17.4	.124	3.1	45	7.9	.21	5.3	9.3	41	.38	9.8	0.032	0.8	11.0	MW	C	Z
0.188	4.78	A-30	.69	17.4	.122	3.1	52	9.1	.20	5.0	10	45	.40	10.1	0.033	0.8	11.0	MW	C	N
0.188	4.78	F-90	.69	17.4	.122	3.1	48	8.4	.15	3.9	7.3	33	.41	10.5	0.033	0.8	11.5	HD	C	Z
0.188	4.78	Q0-7	.69	17.4	.108	2.7	105	18	.11	2.9	12	54	.52	13.2	0.040	1.0	13.0	SPR	CG	Z
0.188	4.78	2809	.72	18.2	.158	4.0	1.8	.31	.55	14	.99	4.4	.17	4.2	0.015	0.4	10.0	MW	C	Z
0.188	4.78	S-1115	.72	18.2	.158	4.0	1.8	.31	.40	10	.72	3.2	.15	3.8	0.015	0.4	9.00	SST	C	N
0.188	4.78	2584	.72	18.2	.156	4.0	1.7	.30	.49	13	.85	3.8	.22	5.7	0.016	0.4	13.0	MW	C	GI
0.188	4.78	10890	.72	18.2	.148	3.8	4.9	.85	.46	12	2.2	9.9	.26	6.6	0.020	0.5	12.0	MW	C	N
0.188	4.78	F-83	.72	18.2	.136	3.5	15	2.7	.33	8.4	5.1	23	.34	8.6	0.026	0.7	12.0	MW	C	Z
0.188	4.78	S-1333	.75	19.1	.166	4.2	.48	.08	.63	16	.30	1.3	.11	2.8	0.011	0.3	9.00	SST	C	N
0.188	4.78	KK-96	.75	19.1	.160	4.1	.93	.16	.57	14	.53	2.3	.18	4.6	0.014	0.4	12.0	SST	C	N
0.188	4.78	U-25	.75	19.1	.158	4.0	.73	.13	.45	11	.33	1.5	.30	7.6	0.015	0.4	19.0	SST	C	N
0.188	4.78	V-72	.75	19.1	.156	4.0	2.1	.36	.56	14	1.1	5.1	.19	4.9	0.016	0.4	11.0	MW	C	N
0.188	4.78	3927	.75	19.1	.154	3.9	2.7	.48	.55	14	1.5	6.6	.20	5.						



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	UU-5	.81	20.6	.152	3.9	3.4	.60	.36	9.2	1.2	5.5	.20	5.0	0.018	0.5	10.0	SST	C	N
0.188	4.78	II-26	.81	20.6	.142	3.6	8.5	1.5	.45	11	3.8	17	.32	8.0	0.023	0.6	12.8	MW	C	N
0.188	4.78	M-40	.81	20.6	.138	3.5	24	4.1	.19	4.9	4.6	20	.19	4.8	0.025	0.6	7.50	MW	CG	Z
0.188	4.78	A14-16	.81	20.6	.136	3.5	10	1.8	.34	8.7	3.6	16	.47	11.9	0.026	0.7	17.0	MW	C	Z
0.188	4.78	2970	.81	20.6	.134	3.4	16	2.7	.37	9.3	5.7	25	.41	10.3	0.027	0.7	14.0	MW	C	GI
0.188	4.78	KK-99	.81	20.6	.098	2.5	179	31	.09	2.4	17	74	.61	15.4	0.045	1.1	13.5	SPR	CG	Z
0.188	4.78	A10-57	.84	21.4	.160	4.1	.86	.15	.71	18	.61	2.7	.14	3.5	0.014	0.4	8.75	PB	C	N
0.188	4.78	B5-70	.84	21.4	.156	4.0	2.2	.38	.60	15	1.3	5.8	.18	4.7	0.016	0.4	10.5	MW	C	N
0.188	4.78	KK-12	.84	21.4	.152	3.9	1.7	.30	.50	13	.85	3.8	.34	8.7	0.018	0.5	18.0	SST	C	N
0.188	4.78	3026	.84	21.4	.138	3.5	12	2.1	.39	9.9	4.6	20	.36	9.0	0.025	0.6	13.3	MW	C	Z
0.188	4.78	F-80	.84	21.4	.136	3.5	13	2.3	.40	10	5.1	23	.39	9.9	0.026	0.7	14.0	MW	C	Z
0.188	4.78	F-75	.84	21.4	.122	3.1	35	6.2	.21	5.3	7.3	33	.53	13.4	0.033	0.8	15.0	HD	C	Z
0.188	4.78	GG-49	.88	22.2	.160	4.1	.32	.06	.43	11	.14	.61	.45	11.4	0.014	0.4	31.0	SST	C	N
0.188	4.78	922	.88	22.2	.156	4.0	1.3	.24	.60	15	.81	3.6	.27	6.9	0.016	0.4	16.0	MW	C	Z
0.188	4.78	B14-61	.88	22.2	.152	3.9	3.1	.53	.60	15	1.8	8.2	.21	5.4	0.018	0.5	10.8	MW	C	Z
0.188	4.78	S-1161	.88	22.2	.144	3.7	6.5	1.1	.34	8.6	2.2	9.8	.29	7.3	0.022	0.6	12.0	SST	C	N
0.188	4.78	S-1340	.88	22.2	.142	3.6	9.9	1.7	.25	6.5	2.5	11	.25	6.4	0.023	0.6	10.0	SST	C	N
0.188	4.78	B1-18	.88	22.2	.136	3.5	12	2.2	.41	11	5.1	23	.38	9.7	0.026	0.7	14.8	MW	CG	N
0.188	4.78	L-87	.88	22.2	.126	3.2	31	5.5	.27	6.9	8.5	38	.43	11.0	0.031	0.8	13.0	MW	C	N
0.188	4.78	S-712	.88	22.2	.124	3.1	26	4.5	.24	6.2	6.2	28	.54	13.6	0.032	0.8	15.8	SST	C	N
0.188	4.78	B12-27	.88	22.2	.124	3.1	27	4.8	.24	6.2	6.7	30	.53	13.4	0.032	0.8	16.5	SPR	CG	Z
0.188	4.78	O-85	.88	22.2	.110	2.8	67	12	.17	4.3	11	50	.70	17.8	0.039	1.0	17.0	SPR	C	N
0.188	4.78	J-91	.88	22.2	.108	2.7	77	14	.16	3.9	12	53	.72	18.3	0.040	1.0	17.0	SPR	C	N
0.188	4.78	B14-23	.91	23.0	.154	3.9	3.0	.53	.52	13	1.6	6.9	.17	4.3	0.017	0.4	10.0	MW	CG	N
0.188	4.78	F-51	.91	23.0	.138	3.5	8.3	1.4	.43	11	3.6	16	.48	12.1	0.025	0.6	18.0	MW	C	Z
0.188	4.78	V-86	.91	23.0	.138	3.5	11	1.9	.43	11	4.6	20	.38	9.7	0.025	0.6	14.3	MW	C	N
0.188	4.78	J-58	.91	23.0	.136	3.5	12	2.1	.42	11	5.1	23	.41	10.5	0.026	0.7	14.9	MW	C	Z
0.188	4.78	F-77	.91	23.0	.124	3.1	29	5.1	.23	5.9	6.7	30	.54	13.8	0.032	0.8	16.0	SPR	C	Z
0.188	4.78	FF-65	.94	23.8	.152	3.9	1.5	.26	.56	14	.85	3.8	.38	9.6	0.018	0.5	20.0	SST	C	N
0.188	4.78	S-1334	.94	23.8	.142	3.6	5.7	.99	.44	11	2.5	11	.39	9.9	0.023	0.6	16.0	SST	C	N
0.188	4.78	V-27	.94	23.8	.142	3.6	6.1	1.1	.52	13	3.2	14	.41	10.5	0.023	0.6	17.0	MW	C	N
0.188	4.78	F-95	.94	23.8	.124	3.1	25	4.4	.26	6.7	6.7	30	.61	15.4	0.032	0.8	18.0	SPR	C	Z
0.188	4.78	H-67	.97	24.6	.144	3.7	4.1	.73	.53	14	2.2	9.8	.39	9.9	0.022	0.6	17.8	SST	CG	N
0.188	4.78	Q-55	1.00	25.4	.166	4.2	.17	.03	.77	20	.13	.59	.23	5.8	0.011	0.3	21.0	SST	C	N
0.188	4.78	152-A	1.00	25.4	.162	4.1	.99	.17	.79	20	.78	3.5	.14	3.6	0.013	0.3	9.75	MW	C	Z
0.188	4.78	153-A	1.00	25.4	.160	4.1	1.2	.22	.78	20	.97	4.3	.16	4.1	0.014	0.4	10.5	MW	C	Z
0.188	4.78	Q-69	1.00	25.4	.160	4.1	.43	.07	.63	16	.27	1.2	.37	9.4	0.014	0.4	26.5	MW	CG	N
0.188	4.78	353-A	1.00	25.4	.156	4.0	2.0	.35	.66	17	1.3	5.8	.20	5.1	0.016	0.4	11.5	MW	C	Z
0.188	4.78	N-37	1.00	25.4	.156	4.0	2.3	.41	.56	14	1.3	5.8	.18	4.5	0.016	0.4	10.0	MW	C	Z
0.188	4.78	352-A	1.00	25.4	.152	3.9	3.0	.52	.62	16	1.8	8.2	.24	6.2	0.018	0.5	12.5	MW	C	Z
0.188	4.78	B15-2	1.00	25.4	.152	3.9	2.0	.35	.61	15	1.2	5.5	.28	7.1	0.018	0.5	15.5	SST	CG	N
0.188	4.78	154-A	1.00	25.4	.148	3.8	4.2	.74	.60	15	2.5	11	.29	7.4	0.020	0.5	13.5	MW	C	Z
0.188	4.78	FF-57	1.00	25.4	.148	3.8	2.7	.47	.62	16	1.7	7.4	.36	9.1	0.020	0.5	18.0	SST	CG	N
0.188	4.78	V-9	1.00	25.4	.148	3.8	2.7	.47	.62	16	1.7	7.4	.38	9.7	0.020	0.5	18.0	SST	C	N
0.188	4.78	10171	1.00	25.4	.146	3.7	3.5	.61	.58	15	2.0	8.9	.43	10.8	0.021	0.5	19.3	MW	C	Z
0.188	4.78	2597	1.00	25.4	.146	3.7	4.2	.74	.63	16	2.7	12	.37	9.3	0.021	0.5	16.5	MW	C	Z
0.188	4.78	K-85	1.00	25.4	.144	3.7	6.8	1.2	.49	12	3.3	15	.31	7.8	0.022	0.6	13.0	MW	C	Z
0.188	4.78	155-A	1.00	25.4	.142	3.6	7.0	1.2	.54	14	3.8	17	.36	9.2	0.023	0.6	14.8	MW	C	Z
0.188	4.78	3692	1.00	25.4	.140	3.6	6.5	1.1	.52	13	3.4	15	.48	12.2	0.024	0.6	19.0	MW	C	Z
0.188	4.78	L-88	1.00	25.4	.138	3.5	9.4	1.7	.48	12	4.6	20	.40	10.2	0.025	0.6	16.0	MW	CG	N
0.188	4.78	LL-55	1.00	25.4	.138	3.5	10	1.8	.45	11	4.6	20	.38	9.5	0.025	0.6	15.0	MW	CG	Z
0.188	4.78	B15-52	1.00	25.4	.138	3.5	9.3	1.6	.49	12	4.6	20	.40	10.2	0.025	0.6	16.0	MW	CG	N
0.188	4.78	156-A	1.00	25.4	.132	3.4	15	2.7	.42	11	6.3	28	.48	12.3	0.028	0.7	16.3	MW	C	Z
0.188	4.78	S-713	1.00	25.4	.124	3.1	22	3.9	.28	7.2	6.2	28	.61	15.4	0.032	0.8	18.0	SST	C	N
0.188	4.78	B10-20	1.00	25.4	.124	3.1	26	4.5	.26	6.6	6.7	30	.59	15.0	0.032	0.8	17.5	SPR	C/G	N
0.188	4.78	1509	1.03	26.2	.144	3.7	8.2	1.4	.41	10	3.3	15	.26	6.7	0.022	0.6	11.0	MW	C	Z
0.188	4.78	G-72	1.03	26.2	.144	3.7	4.6	.81	.61	16	2.8	13	.42	10.6	0.022	0.6	18.0	MW	C	Z
0.188	4.78	A-88	1.06	27.0	.158	4.0	.73	.13	.76	19	.56	2.5	.30	7.6	0.015	0.4	19.0	SST	C	N
0.188	4.78	YY-10	1.06	27.0	.154	3.9	1.8	.32												



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.188	4.78	154-B	1.38	34.9	.148	3.8	3.0	.53	.83	21	2.5	11	.38	9.7	0.020	0.5	18.0	MW	C	Z
0.188	4.78	GG-28	1.38	34.9	.148	3.8	2.7	.47	.93	24	2.5	11	.40	10.2	0.020	0.5	20.0	MW	CG	N
0.188	4.78	B9-70	1.38	34.9	.148	3.8	2.9	.50	.88	22	2.5	11	.38	9.7	0.020	0.5	19.0	MW	CG	Z
0.188	4.78	Q-19	1.38	34.9	.144	3.7	4.1	.72	.81	21	3.3	15	.46	11.7	0.022	0.6	20.0	MW	C	Z
0.188	4.78	155-B	1.38	34.9	.142	3.6	5.0	.87	.76	19	3.8	17	.48	12.3	0.023	0.6	20.0	MW	C	Z
0.188	4.78	S-1157	1.38	34.9	.138	3.5	6.4	1.1	.48	12	3.1	14	.53	13.3	0.025	0.6	20.0	SST	C	N
0.188	4.78	156-B	1.38	34.9	.132	3.4	11	1.9	.59	15	6.3	28	.65	16.5	0.028	0.7	22.3	MW	C	Z
0.188	4.78	12024	1.41	35.7	.150	3.8	2.3	.40	.63	16	1.4	6.4	.34	8.7	0.019	0.5	17.0	SST	C	N
0.188	4.78	S-1105	1.44	36.5	.152	3.9	.94	.16	.86	22	.81	3.6	.58	14.6	0.018	0.5	31.0	SST	C	N
0.188	4.78	J-74	1.44	36.5	.138	3.5	5.6	.98	.54	14	3.1	14	.56	14.3	0.025	0.6	22.5	SST	CG	N
0.188	4.78	A10-61	1.44	36.5	.136	3.5	5.2	.91	.66	17	3.4	15	.78	19.8	0.026	0.7	29.0	SST	C	N
0.188	4.78	S-1317	1.44	36.5	.134	3.4	7.5	1.3	.51	13	3.8	17	.63	16.1	0.027	0.7	23.5	SST	CG	N
0.188	4.78	S-1071	1.44	36.5	.132	3.4	8.0	1.4	.53	14	4.2	19	.76	19.2	0.028	0.7	26.0	SST	C	N
0.188	4.78	923	1.50	38.1	.148	3.8	2.1	.38	.98	25	2.1	9.4	.52	13.2	0.020	0.5	25.0	MW	C	Z
0.188	4.78	B2-17	1.50	38.1	.148	3.8	1.8	.31	.90	23	1.6	7.2	.60	15.2	0.020	0.5	29.0	MW	C	N
0.188	4.78	11194	1.50	38.1	.138	3.5	5.6	.98	.54	14	3.1	14	.56	14.3	0.025	0.6	22.5	SST	CG	N
0.188	4.78	11264	1.50	38.1	.124	3.1	19	3.4	.49	12	9.3	41	.76	19.3	0.032	0.8	22.8	MW	C	N
0.188	4.78	11206	1.56	39.7	.138	3.5	5.8	1.0	.53	13	3.1	14	.55	14.0	0.025	0.6	22.0	SST	CG	N
0.188	4.78	Z-3	1.63	41.3	.168	4.3	.15	.03	1.4	36	.21	.95	.20	5.1	0.010	0.3	19.0	MW	C	N
0.188	4.78	11240	1.63	41.3	.128	3.3	11	1.9	.71	18	7.7	34	.90	22.9	0.030	0.8	29.0	MW	C	Z
0.188	4.78	N-122	1.69	42.8	.148	3.8	2.5	.43	1.0	26	2.5	11	.46	11.7	0.020	0.5	22.0	MW	C	N
0.188	4.78	EE-47	1.69	42.8	.128	3.3	25	4.3	.31	8.0	7.7	34	.45	11.4	0.030	0.8	14.0	MW	C	N
0.188	4.78	152-C	1.75	44.5	.162	4.1	.56	.10	1.4	35	.78	3.5	.22	5.5	0.013	0.3	15.8	MW	C	Z
0.188	4.78	153-C	1.75	44.5	.160	4.1	.69	.12	1.4	36	.97	4.3	.26	6.5	0.014	0.4	17.3	MW	C	Z
0.188	4.78	353-C	1.75	44.5	.156	4.0	1.1	.19	1.2	30	1.3	5.8	.32	8.1	0.016	0.4	19.0	MW	C	Z
0.188	4.78	352-C	1.75	44.5	.152	3.9	1.7	.29	1.1	28	1.8	8.2	.39	9.9	0.018	0.5	20.8	MW	C	Z
0.188	4.78	154-C	1.75	44.5	.148	3.8	2.3	.41	1.1	27	2.5	11	.48	12.1	0.020	0.5	22.8	MW	C	Z
0.188	4.78	2503	1.75	44.5	.148	3.8	3.5	.61	.73	18	2.5	11	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.188	4.78	NN-34	1.75	44.5	.148	3.8	2.1	.37	1.2	30	2.5	11	.52	13.2	0.020	0.5	25.0	MW	C	Z
0.188	4.78	PP-84	1.75	44.5	.146	3.7	2.4	.42	1.2	29	2.8	12	.60	15.2	0.021	0.5	27.5	MW	C	N
0.188	4.78	155-C	1.75	44.5	.142	3.6	3.9	.68	.97	25	3.8	17	.60	15.2	0.023	0.6	25.0	MW	C	Z
0.188	4.78	11407	1.75	44.5	.136	3.5	6.4	1.1	.79	20	5.1	23	.70	17.8	0.026	0.7	26.0	MW	C	Z
0.188	4.78	156-C	1.75	44.5	.132	3.4	8.3	1.5	.76	19	6.3	28	.81	20.6	0.028	0.7	28.0	MW	C	Z
0.188	4.78	A15-48	1.75	44.5	.122	3.1	25	4.4	.27	6.9	6.8	30	.61	15.5	0.033	0.8	18.5	SST	CG	N
0.188	4.78	10003	1.88	47.6	.142	3.6	4.4	.77	.86	22	3.8	17	.52	13.3	0.023	0.6	22.8	MW	CG	Z
0.188	4.78	2631	1.88	47.6	.130	3.3	8.3	1.5	.84	21	7.0	31	.96	24.3	0.029	0.7	33.0	MW	CG	Z
0.188	4.78	Y-86	1.88	47.6	.122	3.1	18	3.2	.40	10	7.3	33	.94	23.9	0.033	0.8	27.5	SPR	C	N
0.188	4.78	S-1351	1.88	47.6	.118	3.0	24	4.3	.32	8.1	7.7	34	.84	21.3	0.035	0.9	24.0	SST	CG	N
0.188	4.78	N-50	1.94	49.2	.138	3.5	4.7	.83	.97	25	4.6	20	.78	19.7	0.025	0.6	30.0	MW	C	Z
0.188	4.78	EE-14	2.00	50.8	.168	4.3	.08	.01	1.7	43	.13	.56	.32	8.1	0.010	0.3	32.0	SST	CG	N
0.188	4.78	B14-42	2.25	57.2	.160	4.1	.50	.09	1.9	49	.96	4.2	.34	8.5	0.014	0.4	23.0	MW	C	Z
0.188	4.78	JJ-87	2.25	57.2	.130	3.3	6.0	1.0	.92	23	5.5	24	1.33	33.9	0.029	0.7	45.0	MW	C	BO
0.188	4.78	3575	2.50	63.5	.130	3.3	5.5	.96	1.1	27	5.8	26	1.45	36.8	0.029	0.7	49.0	MW	C	Z
0.188	4.78	N-27	2.53	64.3	.150	3.8	1.3	.23	1.7	42	2.2	9.6	.61	15.4	0.019	0.5	32.0	MW	CG	N
0.188	4.78	S-1237	2.75	69.9	.128	3.3	5.8	1.0	.89	23	5.2	23	1.44	36.6	0.030	0.8	47.0	SST	C	N
0.188	4.78	TT-44	2.75	69.9	.128	3.3	6.8	1.2	1.1	29	7.7	34	1.41	35.8	0.030	0.8	46.0	MW	C	N
0.188	4.78	B15-43	3.00	76.2	.136	3.5	2.7	.47	1.4	36	3.8	17	1.59	40.3	0.026	0.7	60.0	MW	C	N
0.188	4.78	VV-54	3.13	79.4	.140	3.6	2.2	.39	1.3	33	2.9	13	1.10	28.0	0.024	0.6	45.0	SST	C	N
0.188	4.78	O-72	4.00	101.6	.148	3.8	1.1	.19	1.6	40	1.7	7.4	.86	21.8	0.020	0.5	42.0	SST	C	N
0.195	4.95	B4-62	.47	11.9	.171	4.3	1.1	.19	.36	9.0	.38	1.7	.07	1.8	0.012	0.3	6.00	SST	CG	N
0.203	5.16	N-75	.13	3.2	.163	4.1	33	5.8	.05	1.1	1.5	6.7	.08	2.0	0.020	0.5	3.00	SST	C	N
0.203	5.16	G-74	.19	4.8	.175	4.4	2.2	.38	.10	2.6	.22	.98	.09	2.2	0.014	0.4	5.25	SST	C	N
0.203	5.16	Z-66	.25	6.4	.187	4.7	.09	.02	.16	4.0	.01	.07	.09	2.3	0.008	0.2	10.5	MW	C	N
0.203	5.16	3706	.25	6.4	.123	3.1	283	50	.04	1.0	11	50	.20	5.1	0.040	1.0	5.00	SPR	CG	Z
0.203	5.16	DD-4	.28	7.1	.169	4.3	1.8	.32	.08	2.0	.14	.63	.20	5.2	0.017	0.4	11.0	SST	C	N
0.203	5.16	V-13	.28	7.1	.143	3.6	65	11	.07	1.9	4.8	22	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.203	5.16	W-29	.28	7.1	.123	3.1	246	43	.04	1.1	11	47	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.203	5.16	10918	.31	7.9	.173	4.4	2.2	.38	.19	4.9	.42	1.9	.12	3.0	0.015	0.4	7.00	MW	C	GI
0.203	5.16	O-109	.31	7.9	.167	4.2	7.9	1.4	.20	5.2	1.6	7.2	.11	2.7	0.018	0.5	5.00			




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEF.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.203	5.16	B18-190	.50	12.7	.181	4.6	.66	.12	.42	11	.28	1.2	.08	2.0	0.011	0.3	6.00	SST	C	N
0.203	5.16	S-1552	.50	12.7	.179	4.5	.99	.17	.36	9.3	.36	1.6	.08	2.1	0.012	0.3	5.75	SST	C	N
0.203	5.16	S-1083	.50	12.7	.175	4.4	.68	.12	.31	7.9	.21	.94	.19	4.8	0.014	0.4	12.5	SST	C	N
0.203	5.16	B12-54	.50	12.7	.175	4.4	.74	.13	.32	8.1	.24	1.1	.18	4.6	0.014	0.4	13.0	MW	CG	N
0.203	5.16	HH-34	.50	12.7	.173	4.4	1.1	.19	.31	7.7	.33	1.5	.20	5.0	0.015	0.4	12.0	MW	C	N
0.203	5.16	H-80	.50	12.7	.165	4.2	4.4	.76	.31	7.8	1.3	5.9	.15	3.9	0.019	0.5	8.00	SST	CG	N
0.203	5.16	B14-4	.50	12.7	.165	4.2	4.0	.70	.30	7.6	1.2	5.4	.20	5.1	0.019	0.5	9.50	MW	C	N
0.203	5.16	G-61	.50	12.7	.163	4.1	5.4	.95	.29	7.3	1.6	6.9	.18	4.6	0.020	0.5	8.00	SST	C	N
0.203	5.16	S-1380	.50	12.7	.159	4.0	9.9	1.7	.21	5.3	2.1	9.2	.18	4.5	0.022	0.6	7.00	SST	C	N
0.203	5.16	B8-21	.50	12.7	.157	4.0	8.6	1.5	.27	6.9	2.3	10	.23	5.8	0.023	0.6	10.0	MW	CG	N
0.203	5.16	NN-93	.50	12.7	.155	3.9	12	2.1	.26	6.6	3.1	14	.24	6.1	0.024	0.6	9.00	MW	C	N
0.203	5.16	O-81	.50	12.7	.155	3.9	18	3.1	.23	5.8	4.0	18	.16	4.1	0.024	0.6	6.75	MW	CG	N
0.203	5.16	N-110	.50	12.7	.153	3.9	18	3.2	.23	6.0	4.2	19	.19	4.8	0.025	0.6	7.50	MW	C	Z
0.203	5.16	G-26	.50	12.7	.143	3.6	28	4.9	.17	4.3	4.8	21	.33	8.4	0.030	0.8	10.0	MW	C	N
0.203	5.16	B15-30	.50	12.7	.139	3.5	38	6.7	.15	3.9	5.8	26	.29	7.3	0.032	0.8	9.00	SST	CG	N
0.203	5.16	Q-7	.50	12.7	.123	3.1	121	21	.09	2.4	11	50	.36	9.1	0.040	1.0	9.00	SPR	CG	Z
0.203	5.16	2501	.53	13.5	.143	3.6	32	5.6	.22	5.7	7.2	32	.30	7.6	0.030	0.8	9.00	MW	C	Z
0.203	5.16	LL-43	.56	14.3	.171	4.3	2.4	.42	.42	11	1.0	4.5	.14	3.7	0.016	0.4	8.00	MW	C	N
0.203	5.16	LL-56	.56	14.3	.171	4.3	2.1	.37	.39	9.8	.80	3.6	.14	3.7	0.016	0.4	8.00	SST	C	N
0.203	5.16	3997	.56	14.3	.161	4.1	7.1	1.2	.36	9.2	2.6	12	.20	5.1	0.021	0.5	8.50	MW	C	Z
0.203	5.16	W-78	.56	14.3	.139	3.5	35	6.0	.17	4.3	5.8	26	.31	7.9	0.032	0.8	9.75	SST	CG	N
0.203	5.16	EE-42	.56	14.3	.137	3.5	43	7.6	.16	4.0	6.8	30	.33	8.4	0.033	0.8	10.0	SPR	CG	N
0.203	5.16	GG-32	.56	14.3	.123	3.1	84	15	.12	3.1	10	45	.44	11.2	0.040	1.0	11.0	SST	CG	N
0.203	5.16	11428	.56	14.3	.101	2.6	427	75	.05	1.2	19	87	.40	10.0	0.051	1.3	7.75	SST	CG	N
0.203	5.16	Q-23	.59	15.1	.167	4.2	2.2	.38	.36	9.1	.78	3.5	.23	5.9	0.018	0.5	13.0	MW	CG	N
0.203	5.16	00-82	.63	15.9	.179	4.5	.48	.08	.48	12	.23	1.0	.14	3.7	0.012	0.3	11.0	MW	C	Z
0.203	5.16	A13-53	.63	15.9	.173	4.4	1.9	.32	.36	9.1	.66	3.0	.12	3.1	0.015	0.4	7.25	SST	C	N
0.203	5.16	2748	.63	15.9	.155	3.9	18	3.2	.22	5.5	4.0	18	.18	4.6	0.024	0.6	6.50	MW	C	Z
0.203	5.16	3782	.63	15.9	.155	3.9	8.3	1.5	.31	8.0	2.6	12	.31	7.9	0.024	0.6	12.0	MW	C	Z
0.203	5.16	B4-10	.63	15.9	.153	3.9	9.1	1.6	.31	7.9	2.8	13	.29	7.3	0.025	0.6	11.5	SST	CG	N
0.203	5.16	A10-23	.63	15.9	.147	3.7	15	2.7	.26	6.5	4.0	18	.32	8.2	0.028	0.7	11.5	SST	CG	N
0.203	5.16	JJ-71	.63	15.9	.123	3.1	142	25	.08	2.0	11	50	.32	8.1	0.040	1.0	8.00	SPR	CG	N
0.203	5.16	MM-3	.69	17.4	.179	4.5	.62	.11	.58	15	.36	1.6	.11	2.7	0.012	0.3	8.00	SST	C	N
0.203	5.16	CC-38	.69	17.4	.173	4.4	.95	.17	.49	12	.47	2.1	.20	5.0	0.015	0.4	12.0	SST	C	N
0.203	5.16	RR-38	.69	17.4	.171	4.3	1.2	.21	.45	11	.54	2.4	.24	6.1	0.016	0.4	14.0	MW	C	Z
0.203	5.16	BB-84	.69	17.4	.149	3.8	18	3.1	.30	7.7	5.3	24	.30	7.5	0.027	0.7	10.0	MW	C	N
0.203	5.16	S-1120	.69	17.4	.147	3.7	17	3.0	.23	6.0	4.0	18	.32	8.2	0.028	0.7	10.5	SST	C	N
0.203	5.16	B10-12	.69	17.4	.131	3.3	175	31	.05	1.2	8.4	37	.18	4.6	0.036	0.9	5.00	SPR	CG	N
0.203	5.16	AA-23	.69	17.4	.123	3.1	85	15	.13	3.4	11	50	.48	12.2	0.040	1.0	12.0	SPR	CG	N
0.203	5.16	O-19	.72	18.2	.153	3.9	11	1.9	.38	9.8	4.2	19	.28	7.0	0.025	0.6	11.0	MW	CG	N
0.203	5.16	AA-1	.72	18.2	.143	3.6	22	3.9	.32	8.2	7.2	32	.36	9.1	0.030	0.8	12.0	MW	CG	N
0.203	5.16	A11-7	.72	18.2	.121	3.1	94	16	.12	3.1	11	51	.45	11.5	0.041	1.0	11.0	SST	CG	N
0.203	5.16	B-95	.75	19.1	.179	4.5	.71	.12	.64	16	.46	2.0	.11	2.7	0.012	0.3	8.00	MW	C	N
0.203	5.16	4291	.75	19.1	.173	4.4	.91	.16	.53	13	.48	2.1	.23	5.7	0.015	0.4	14.0	MW	C	Z
0.203	5.16	4171	.75	19.1	.165	4.2	5.5	.96	.37	9.3	2.0	8.9	.16	4.1	0.019	0.5	7.50	MW	C	Z
0.203	5.16	NN-45	.75	19.1	.163	4.1	1.8	.32	.33	8.4	.61	2.7	.42	10.7	0.020	0.5	20.0	SST	C	N
0.203	5.16	3290	.75	19.1	.159	4.0	7.6	1.3	.41	10	3.1	14	.23	5.9	0.022	0.6	9.50	MW	C	Z
0.203	5.16	Z-83	.75	19.1	.159	4.0	4.4	.76	.42	11	1.8	8.2	.33	8.4	0.022	0.6	15.0	MW	CG	Z
0.203	5.16	B10-17	.75	19.1	.153	3.9	18	3.2	.23	6.0	4.2	19	.19	4.8	0.025	0.6	7.50	MW	CG	N
0.203	5.16	HH-10	.75	19.1	.151	3.8	11	2.0	.28	7.1	3.2	14	.31	7.9	0.026	0.7	11.0	SST	C	N
0.203	5.16	FF-34	.75	19.1	.143	3.6	21	3.7	.23	5.9	4.8	22	.38	9.5	0.030	0.8	11.5	SST	C	N
0.203	5.16	BB-24	.75	19.1	.123	3.1	57	10	.15	3.8	8.5	38	.60	15.2	0.040	1.0	15.0	SST	CG	N
0.203	5.16	3235	.78	19.8	.149	3.8	12	2.0	.38	9.6	4.4	20	.41	10.3	0.027	0.7	14.0	MW	C	Z
0.203	5.16	J-79	.78	19.8	.127	3.2	58	10	.16	4.0	9.2	41	.46	11.6	0.038	1.0	12.0	SST	CG	N
0.203	5.16	II-42	.81	20.6	.163	4.1	4.7	.82	.50	13	2.3	10	.22	5.6	0.020	0.5	10.0	MW	C	GI
0.203	5.16	K-98	.81	20.6	.163	4.1	2.7	.47	.47	12	1.3	5.6	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.203	5.16	FF-49	.81	20.6	.143	3.6	15	2.7	.32	8.0	4.8	22	.45	11.4	0.030	0.8	15.0	SST	CG	N
0.203	5.16	B12-51	.84	21.4	.163	4.1	1.7	.30	.36	9.2	.62	2.8	.48	12.2	0.020	0.5	24.0	MW	CG	N
0.203	5.16	B4-16	.84	21.4	.147	3.7	11	2.0	.35	8.8	4.0	18	.41	10.3	0.028	0.7	14.5	SST	CG	N
0.203	5.16	L-94	.88	22.2	.173	4.4	.52	.09	.52	13	.27	1.2	.36	9.1	0.015	0.4	23.0	MW	C	Z
0.203	5.16	HH-95	.88	22.2	.143	3.6	16	2.9	.30	7.5	4.8	22	.45	11.4	0.030	0.8	14.0	SST	C	N
0.203	5.16	AA-38	.88	22.2	.133	3.4	40	6.9	.20	5.0	7.7	34	.47	12.0	0.035	0.9	13.5	SPR	CG	Z
0.203	5.16	J-31	.94	23.8	.159	4.0	5.2	.90	.60	15	3.1	14	.31	7.8	0.022	0.6	13.0	MW	C	N
0.203	5.16	A-14	.97	24.6	.183	4.6	.09	.02	.74	19	.07	.29	.23	5.8	0.010	0.3	22.0	SST	C	N
0.203	5.16	12535	.97	24.6	.147	3.7	16	2.9	.36	9.1	5.9	26	.36	9.2	0.028	0.7	12.0	MW	C	N
0.203	5.16	2561	1.00	25.4	.167	4.2	2.5	.44	.68	17	1.7	7.6	.23	5.7	0.018	0.5	11.5	MW	C	Z
0.203	5.16	3249	1.00	25.4	.151	3.8	8.8	1.5	.54	14	4.8	21	.43	10.9	0.026	0.7	15.5	MW	C	Z
0.203	5.16	B-1	1.00	25.4	.145	3.7	10	1.8	.42	11	4.4	19	.52	13.3	0.029	0.7	18.0	SST	CG	N
0.203	5.16	S-1500	1.00	25.4	.145	3.7	23	4.1	.19	4.8	4.4	19	.31	7.8	0.029	0.7	11.0	SST	CG	N
0.203	5.16	B2-35	1.00	25.4	.141	3.6	17	3.0	.44	11</										




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.203	5.16	PP-23	1.16	29.4	.133	3.4	29	5.1	.26	6.7	7.7	34	.65	16.4	0.035	0.9	17.5	SPR	C	N
0.203	5.16	12285	1.19	30.2	.123	3.1	61	11	.19	4.7	11	50	.68	17.3	0.040	1.0	16.0	SPR	C	N
0.203	5.16	VV-23	1.22	31.0	.143	3.6	14	2.5	.51	13	7.2	32	.57	14.5	0.030	0.8	18.0	MW	C	N
0.203	5.16	BB-26	1.22	31.0	.143	3.6	10	1.7	.48	12	4.8	22	.66	16.8	0.030	0.8	22.0	SS	CG	N
0.203	5.16	B2-25	1.25	31.8	.157	4.0	5.5	.97	.64	16	3.5	16	.36	9.1	0.023	0.6	14.5	MW	C	Z
0.203	5.16	W-74	1.25	31.8	.143	3.6	9.8	1.7	.49	13	4.8	22	.69	17.5	0.030	0.8	22.0	SST	C	N
0.203	5.16	Q-90	1.31	33.3	.171	4.3	.82	.14	1.0	25	.82	3.7	.31	7.9	0.016	0.4	19.5	MW	CG	N
0.203	5.16	S-481	1.31	33.3	.165	4.2	1.4	.25	.92	23	1.3	5.8	.39	9.9	0.019	0.5	20.5	SST	CG	N
0.203	5.16	3201	1.34	34.1	.163	4.1	2.7	.47	.87	22	2.3	10	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.203	5.16	10754	1.41	35.7	.141	3.6	9.3	1.6	.54	14	5.0	22	.87	22.0	0.031	0.8	27.0	SST	C	N
0.203	5.16	V-5	1.50	38.1	.153	3.9	5.0	.87	.85	22	4.2	19	.58	14.6	0.025	0.6	22.0	MW	C	Z
0.203	5.16	10026	1.50	38.1	.151	3.8	7.4	1.3	.64	16	4.8	21	.49	12.5	0.026	0.7	18.0	MW	C	Z
0.203	5.16	3012	1.56	39.7	.155	3.9	4.6	.81	.87	22	4.0	18	.50	12.8	0.024	0.6	20.0	MW	C	Z
0.203	5.16	2884	1.75	44.5	.159	4.0	2.5	.44	1.2	30	3.0	13	.56	14.2	0.022	0.6	24.5	MW	C	GI
0.203	5.16	10891	1.78	45.2	.153	3.9	3.0	.53	.91	23	2.7	12	.88	22.2	0.025	0.6	35.0	MW	CG	GI
0.203	5.16	12018	2.25	57.2	.101	2.6	107	19	.19	4.9	21	92	1.43	36.3	0.051	1.3	28.0	SPR	CG	Z
0.203	5.16	S-3140	4.00	101.6	.143	3.6	3.3	.57	1.5	38	4.8	22	1.89	48.0	0.030	0.8	62.0	SST	C	N
0.210	5.33	70460	.25	6.4	.174	4.4	11	1.9	.15	3.8	1.7	7.4	.07	1.8	0.018	0.5	4.00	MW	CG	N
0.210	5.33	70460S	.25	6.4	.174	4.4	9.4	1.6	.12	3.0	1.1	4.9	.07	1.8	0.018	0.5	4.00	SST	CG	N
0.210	5.33	70476	.25	6.4	.166	4.2	22	3.8	.14	3.5	3.0	13	.10	2.4	0.022	0.6	4.38	MW	CG	N
0.210	5.33	70476S	.25	6.4	.166	4.2	18	3.2	.11	2.7	2.0	8.9	.10	2.4	0.022	0.6	4.38	SST	CG	N
0.210	5.33	70498	.25	6.4	.158	4.0	41	7.2	.11	2.8	4.6	21	.12	3.0	0.026	0.7	4.50	MW	CG	N
0.210	5.33	70498S	.25	6.4	.158	4.0	35	6.1	.09	2.2	3.1	14	.12	3.0	0.026	0.7	4.50	SST	CG	N
0.210	5.33	70461	.31	7.9	.174	4.4	8.6	1.5	.19	4.9	1.7	7.4	.08	2.1	0.018	0.5	4.50	MW	CG	N
0.210	5.33	70461S	.31	7.9	.174	4.4	7.3	1.3	.15	3.8	1.1	4.9	.08	2.1	0.018	0.5	4.50	SST	CG	N
0.210	5.33	70477	.31	7.9	.166	4.2	17	2.9	.18	4.5	3.0	13	.11	2.8	0.022	0.6	5.00	MW	CG	N
0.210	5.33	70477S	.31	7.9	.166	4.2	14	2.5	.14	3.6	2.0	8.9	.11	2.8	0.022	0.6	5.00	SST	CG	N
0.210	5.33	70499	.31	7.9	.158	4.0	32	5.5	.15	3.7	4.6	21	.14	3.5	0.026	0.7	5.38	MW	CG	N
0.210	5.33	70499S	.31	7.9	.158	4.0	27	4.7	.12	2.9	3.1	14	.14	3.5	0.026	0.7	5.38	SST	CG	N
0.210	5.33	70462	.38	9.7	.174	4.4	6.8	1.2	.24	6.2	1.7	7.4	.09	2.3	0.018	0.5	5.13	MW	CG	N
0.210	5.33	70462S	.38	9.7	.174	4.4	5.8	1.0	.19	4.8	1.1	4.9	.09	2.3	0.018	0.5	5.13	SST	CG	N
0.210	5.33	70478	.38	9.7	.166	4.2	13	2.3	.22	5.7	3.0	13	.13	3.2	0.022	0.6	5.75	MW	CG	N
0.210	5.33	70478S	.38	9.7	.166	4.2	11	2.0	.18	4.5	2.0	8.9	.13	3.2	0.022	0.6	5.75	SST	CG	N
0.210	5.33	70500	.38	9.7	.158	4.0	25	4.4	.18	4.7	4.6	21	.16	4.1	0.026	0.7	6.25	MW	CG	N
0.210	5.33	70500S	.38	9.7	.158	4.0	21	3.7	.15	3.7	3.1	14	.16	4.1	0.026	0.7	6.25	SST	CG	N
0.210	5.33	70463	.44	11.2	.174	4.4	5.8	1.0	.29	7.3	1.7	7.4	.10	2.6	0.018	0.5	5.63	MW	CG	N
0.210	5.33	70463S	.44	11.2	.174	4.4	4.9	.86	.22	5.7	1.1	4.9	.10	2.6	0.018	0.5	5.63	SST	CG	N
0.210	5.33	70479	.44	11.2	.166	4.2	11	2.0	.26	6.7	3.0	13	.14	3.6	0.022	0.6	6.50	MW	CG	N
0.210	5.33	70479S	.44	11.2	.166	4.2	9.7	1.7	.21	5.2	2.0	8.9	.14	3.6	0.022	0.6	6.50	SST	CG	N
0.210	5.33	70501	.44	11.2	.158	4.0	21	3.7	.22	5.5	4.6	21	.18	4.6	0.026	0.7	7.00	MW	CG	N
0.210	5.33	70501S	.44	11.2	.158	4.0	18	3.1	.17	4.4	3.1	14	.18	4.6	0.026	0.7	7.00	SST	CG	N
0.210	5.33	70464	.50	12.7	.174	4.4	5.1	.89	.33	8.3	1.7	7.4	.11	2.8	0.018	0.5	6.13	MW	CG	N
0.210	5.33	70464S	.50	12.7	.174	4.4	4.3	.76	.25	6.5	1.1	4.9	.11	2.8	0.018	0.5	6.13	SST	CG	N
0.210	5.33	70480	.50	12.7	.166	4.2	9.9	1.7	.30	7.7	3.0	13	.16	4.0	0.022	0.6	7.13	MW	CG	N
0.210	5.33	70480S	.50	12.7	.166	4.2	8.4	1.5	.24	6.0	2.0	8.9	.16	4.0	0.022	0.6	7.13	SST	CG	N
0.210	5.33	70502	.50	12.7	.158	4.0	18	3.2	.25	6.4	4.6	21	.20	5.1	0.026	0.7	7.75	MW	CG	N
0.210	5.33	70502S	.50	12.7	.158	4.0	16	2.7	.20	5.1	3.1	14	.20	5.1	0.026	0.7	7.75	SST	CG	N
0.210	5.33	70465	.56	14.2	.174	4.4	4.5	.79	.37	9.4	1.7	7.4	.12	3.1	0.018	0.5	6.75	MW	CG	N
0.210	5.33	70465S	.56	14.2	.174	4.4	3.8	.67	.29	7.3	1.1	4.9	.12	3.1	0.018	0.5	6.75	SST	CG	N
0.210	5.33	70481	.56	14.2	.166	4.2	8.7	1.5	.35	8.8	3.0	13	.17	4.4	0.022	0.6	7.88	MW	CG	N
0.210	5.33	70481S	.56	14.2	.166	4.2	7.4	1.3	.27	6.9	2.0	8.9	.17	4.4	0.022	0.6	7.88	SST	CG	N
0.210	5.33	70503	.56	14.2	.158	4.0	16	2.8	.29	7.3	4.6	21	.22	5.6	0.026	0.7	8.50	MW	CG	N
0.210	5.33	70503S	.56	14.2	.158	4.0	14	2.4	.23	5.7	3.1	14	.22	5.6	0.026	0.7	8.50	SST	CG	N
0.210	5.33	70466	.63	16.0	.174	4.4	4.0	.70	.41	11	1.7	7.4	.13	3.4	0.018	0.5	7.38	MW	CG	N
0.210	5.33	70466S	.63	16.0	.174	4.4	3.4	.60	.32	8.2	1.1	4.9	.13	3.4	0.018	0.5	7.38	SST	CG	N
0.210	5.33	70482	.63	16.0	.166	4.2	7.8	1.4	.39	9.8	3.0	13	.19	4.7	0.022	0.6	8.50	MW	CG	N
0.210	5.33	70482S	.63	16.0	.166	4.2	6.6	1.2	.30	7.7	2.0	8.9	.19	4.7	0.022	0.6	8.50	SST	CG	N
0.210	5.33	70504	.63	16.0	.158	4.0	14	2.5	.33	8.3	4.6	21	.24	6.2	0.026	0.7	9.38	MW	CG	N
0.210	5.33	70504S	.63	16.0	.158	4.0	12	2.1	.26	6.5	3.1	14	.24	6.2	0.026	0.7	9.38	SST	CG	N
0.210	5.33	12549	.67	17.1	.170	4.3	5.6	.98	.41	10	2.3	10	.18	4.6	0.020	0.5	8.00	MW	C	Z
0.210	5.33	70467	.69	17.5	.174	4.4	3.6	.63	.46	12	1.7	7.4	.14	3.6	0.018	0.5	7.88	MW	CG	N
0.210	5.33	70467S	.69	17.5	.174	4.4	3.1	.54	.36	9.2	1.1	4.9	.14	3.6	0.018	0.5	7.88	SST	CG	N
0.210	5.33	70483	.69	17.5	.166	4.2	6.9	1.2	.43	11	3.0	13	.21	5.2	0.022	0.6	9.38	MW	CG	N
0.210	5.33	70483S	.69	17.5	.166	4.2	5.9	1.0	.34	8.6	2.0	8.9	.21	5.2	0.022	0.6	9.38	SST	CG	N
0.210	5.33	70505	.69	17.5	.158	4.0	13	2.3	.36	9.1	4.6	21	.27	6.8	0.026	0.7	10.3	MW	CG	N
0.210	5.33	70505S	.69	17.5	.158	4.0	11	1.9	.28	7.2	3.1	14	.27	6.8	0.026	0.7	10.3	SST	CG	N
0.210	5.33	70468	.75	19.1	.174	4.4	3.3	.58	.50	13	1.7	7.4	.15	3.9	0.018	0.5	8.50	MW	CG	N
0.210	5.33	70468S	.75	19.1	.174	4.4	2.8	.49	.39	10	1.1	4.9	.15	3.9	0.018	0.5	8.50	SST	CG	N



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.210	5.33	70486	.88	22.4	.166	4.2	5.8	1.0	.52	13	3.0	13	.24	6.0	0.022	0.6	10.8	MW	CG	N
0.210	5.33	70486S	.88	22.4	.166	4.2	4.9	.86	.40	10	2.0	8.9	.24	6.0	0.022	0.6	10.8	SST	CG	N
0.210	5.33	70508	.88	22.4	.158	4.0	11	1.8	.44	11	4.6	21	.31	7.9	0.026	0.7	12.0	MW	CG	N
0.210	5.33	70508S	.88	22.4	.158	4.0	8.9	1.6	.35	8.8	3.1	14	.31	7.9	0.026	0.7	12.0	SST	CG	N
0.210	5.33	70488	.94	23.9	.166	4.2	5.3	.93	.57	14	3.0	13	.26	6.5	0.022	0.6	11.6	MW	CG	N
0.210	5.33	70488S	.94	23.9	.166	4.2	4.5	.79	.44	11	2.0	8.9	.26	6.5	0.022	0.6	11.6	SST	CG	N
0.210	5.33	70510	.94	23.9	.158	4.0	9.7	1.7	.48	12	4.6	21	.33	8.5	0.026	0.7	12.9	MW	CG	N
0.210	5.33	70510S	.94	23.9	.158	4.0	8.2	1.4	.37	9.5	3.1	14	.33	8.5	0.026	0.7	12.9	SST	CG	N
0.210	5.33	70471	1.00	25.4	.174	4.4	2.4	.42	.69	18	1.7	7.4	.20	5.0	0.018	0.5	10.9	MW	CG	N
0.210	5.33	70471S	1.00	25.4	.174	4.4	2.0	.36	.54	14	1.1	4.9	.20	5.0	0.018	0.5	10.9	SST	CG	N
0.210	5.33	70489	1.00	25.4	.166	4.2	4.7	.81	.64	16	3.0	13	.28	7.2	0.022	0.6	12.9	MW	CG	N
0.210	5.33	70489S	1.00	25.4	.166	4.2	4.0	.69	.50	13	2.0	8.9	.28	7.2	0.022	0.6	12.9	SST	CG	N
0.210	5.33	70511	1.00	25.4	.158	4.0	8.6	1.5	.54	14	4.6	21	.37	9.4	0.026	0.7	14.3	MW	CG	N
0.210	5.33	70511S	1.00	25.4	.158	4.0	7.3	1.3	.42	11	3.1	14	.37	9.4	0.026	0.7	14.3	SST	CG	N
0.210	5.33	70491	1.13	28.7	.166	4.2	4.4	.77	.68	17	3.0	13	.30	7.5	0.022	0.6	13.5	MW	CG	N
0.210	5.33	70491S	1.13	28.7	.166	4.2	3.7	.65	.53	14	2.0	8.9	.30	7.5	0.022	0.6	13.5	SST	CG	N
0.210	5.33	70513	1.13	28.7	.158	4.0	8.0	1.4	.58	15	4.6	21	.39	10.0	0.026	0.7	15.1	MW	CG	N
0.210	5.33	70513S	1.13	28.7	.158	4.0	6.8	1.2	.45	12	3.1	14	.39	10.0	0.026	0.7	15.1	SST	CG	N
0.210	5.33	70472	1.25	31.8	.174	4.4	1.9	.33	.87	22	1.7	7.4	.24	6.1	0.018	0.5	13.3	MW	CG	N
0.210	5.33	70472S	1.25	31.8	.174	4.4	1.6	.28	.68	17	1.1	4.9	.24	6.1	0.018	0.5	13.3	SST	CG	N
0.210	5.33	70492	1.25	31.8	.166	4.2	3.7	.65	.81	21	3.0	13	.35	8.8	0.022	0.6	15.8	MW	CG	N
0.210	5.33	70492S	1.25	31.8	.166	4.2	3.1	.55	.63	16	2.0	8.9	.35	8.8	0.022	0.6	15.8	SST	CG	N
0.210	5.33	70514	1.25	31.8	.158	4.0	6.8	1.2	.68	17	4.6	21	.46	11.6	0.026	0.7	17.5	MW	CG	N
0.210	5.33	70514S	1.25	31.8	.158	4.0	5.8	1.0	.53	14	3.1	14	.46	11.6	0.026	0.7	17.5	SST	CG	N
0.210	5.33	70494	1.38	35.1	.166	4.2	3.6	.63	.83	21	3.0	13	.35	9.0	0.022	0.6	16.1	MW	CG	N
0.210	5.33	70494S	1.38	35.1	.166	4.2	3.1	.54	.65	17	2.0	8.9	.35	9.0	0.022	0.6	16.1	SST	CG	N
0.210	5.33	70516	1.38	35.1	.158	4.0	6.5	1.1	.71	18	4.6	21	.47	12.1	0.026	0.7	18.3	MW	CG	N
0.210	5.33	70516S	1.38	35.1	.158	4.0	5.5	.97	.56	14	3.1	14	.47	12.1	0.026	0.7	18.3	SST	CG	N
0.210	5.33	70473	1.50	38.1	.174	4.4	1.6	.28	1.0	26	1.7	7.4	.28	7.0	0.018	0.5	15.4	MW	CG	N
0.210	5.33	70473S	1.50	38.1	.174	4.4	1.4	.24	.81	21	1.1	4.9	.28	7.0	0.018	0.5	15.4	SST	CG	N
0.210	5.33	70495	1.50	38.1	.166	4.2	3.0	.53	.99	25	3.0	13	.41	10.5	0.022	0.6	18.8	MW	CG	N
0.210	5.33	70495S	1.50	38.1	.166	4.2	2.6	.45	.78	20	2.0	8.9	.41	10.5	0.022	0.6	18.8	SST	CG	N
0.210	5.33	70517	1.50	38.1	.158	4.0	5.6	.99	.82	21	4.6	21	.54	13.7	0.026	0.7	20.8	MW	CG	N
0.210	5.33	70517S	1.50	38.1	.158	4.0	4.8	.84	.65	16	3.1	14	.54	13.7	0.026	0.7	20.8	SST	CG	N
0.210	5.33	70474	1.75	44.5	.174	4.4	1.4	.25	1.2	30	1.7	7.4	.31	7.9	0.018	0.5	17.3	MW	CG	N
0.210	5.33	70474S	1.75	44.5	.174	4.4	1.2	.21	.93	24	1.1	4.9	.31	7.9	0.018	0.5	17.3	SST	CG	N
0.210	5.33	70496	1.75	44.5	.166	4.2	2.9	.51	1.0	26	3.0	13	.43	10.9	0.022	0.6	19.5	MW	CG	N
0.210	5.33	70496S	1.75	44.5	.166	4.2	2.5	.43	.81	21	2.0	8.9	.43	10.9	0.022	0.6	19.5	SST	CG	N
0.210	5.33	70518	1.75	44.5	.158	4.0	5.1	.89	.91	23	4.6	21	.59	14.9	0.026	0.7	22.6	MW	CG	N
0.210	5.33	70518S	1.75	44.5	.158	4.0	4.3	.76	.71	18	3.1	14	.59	14.9	0.026	0.7	22.6	SST	CG	N
0.210	5.33	70475	2.00	50.8	.174	4.4	1.2	.21	1.4	35	1.7	7.4	.36	9.0	0.018	0.5	19.8	MW	CG	N
0.210	5.33	70475S	2.00	50.8	.174	4.4	1.0	.18	1.1	27	1.1	4.9	.36	9.0	0.018	0.5	19.8	SST	CG	N
0.210	5.33	70497	2.00	50.8	.166	4.2	2.5	.44	1.2	30	3.0	13	.49	12.4	0.022	0.6	22.3	MW	CG	N
0.210	5.33	70497S	2.00	50.8	.166	4.2	2.1	.37	.94	24	2.0	8.9	.49	12.4	0.022	0.6	22.3	SST	CG	N
0.210	5.33	70519	2.00	50.8	.158	4.0	4.5	.79	1.0	26	4.6	21	.66	16.8	0.026	0.7	25.4	MW	CG	N
0.210	5.33	70519S	2.00	50.8	.158	4.0	3.8	.67	.81	21	3.1	14	.66	16.8	0.026	0.7	25.4	SST	CG	N
0.219	5.56	S-863	.22	5.6	.179	4.5	13	2.3	.11	2.8	1.4	6.4	.10	2.5	0.020	0.5	4.00	SST	C	N
0.219	5.56	MM-39	.25	6.4	.179	4.5	15	2.6	.15	3.8	2.2	9.7	.10	2.5	0.020	0.5	4.00	MW	C	Z
0.219	5.56	II-38	.25	6.4	.173	4.4	15	2.7	.11	2.8	1.7	7.7	.14	3.5	0.023	0.6	5.00	SST	C	N
0.219	5.56	G-21	.31	7.9	.197	5.0	.26	.05	.18	4.6	.05	.21	.13	3.4	0.011	0.3	11.0	MW	C	BO
0.219	5.56	S-1531	.31	7.9	.195	5.0	1.2	.21	.25	6.2	.29	1.3	.07	1.7	0.012	0.3	4.50	SST	C	N
0.219	5.56	S-1547	.31	7.9	.193	4.9	1.6	.29	.24	6.1	.39	1.7	.07	1.8	0.013	0.3	4.50	SST	C	N
0.219	5.56	A-15	.31	7.9	.179	4.5	5.1	.89	.15	3.9	.77	3.4	.16	4.1	0.020	0.5	7.00	SST	C	N
0.219	5.56	B9-29	.31	7.9	.177	4.5	14	2.5	.17	4.4	2.5	11	.09	2.4	0.021	0.5	4.50	MW	CG	N
0.219	5.56	I-67	.31	7.9	.169	4.3	19	3.4	.14	3.5	2.6	12	.18	4.4	0.025	0.6	6.00	MW	C	GI
0.219	5.56	A10-18	.31	7.9	.167	4.2	27	4.7	.11	2.8	3.0	13	.13	3.3	0.026	0.7	5.00	SST	CG	N
0.219	5.56	S-1553	.33	8.3	.195	5.0	1.2	.20	.26	6.7	.31	1.4	.07	1.7	0.012	0.3	4.50	SST	C	N
0.219	5.56	B14-38	.34	8.7	.179	4.5	5.8	1.0	.18	4.6	1.1	4								



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.219	5.56	H-71	.44	11.1	.141	3.6	107	19	.09	2.3	9.9	44	.29	7.3	0.039	1.0	7.33	SPR	CG	N
0.219	5.56	HH-46	.44	11.1	.139	3.5	112	20	.09	2.3	9.9	44	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.219	5.56	L-29	.44	11.1	.139	3.5	214	37	.05	1.3	11	47	.20	5.1	0.040	1.0	5.00	SPR	CG	Z
0.219	5.56	XX-21	.47	11.9	.145	3.7	78	14	.10	2.6	8.0	35	.30	7.5	0.037	0.9	7.00	SST	C	N
0.219	5.56	B15-4	.47	11.9	.145	3.7	72	13	.12	3.0	8.5	38	.31	7.8	0.037	0.9	8.25	SPR	CG	N
0.219	5.56	2703	.47	11.9	.143	3.6	126	22	.10	2.6	13	57	.27	6.8	0.038	1.0	6.00	MW	C	Z
0.219	5.56	A11-20	.47	11.9	.133	3.4	200	35	.06	1.6	12	54	.30	7.6	0.043	1.1	6.00	SST	C	N
0.219	5.56	EE-86	.50	12.7	.191	4.9	.46	.08	.29	7.4	.13	.60	.21	5.3	0.014	0.4	14.0	SST	C	N
0.219	5.56	B-66	.50	12.7	.187	4.7	1.7	.30	.35	8.8	.60	2.7	.15	3.9	0.016	0.4	8.50	MW	C	N
0.219	5.56	10314	.50	12.7	.179	4.5	7.3	1.3	.30	7.6	2.2	9.7	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.219	5.56	3161	.50	12.7	.179	4.5	5.1	.89	.33	8.3	1.6	7.3	.18	4.4	0.020	0.5	7.75	MW	C	Z
0.219	5.56	H-20	.50	12.7	.179	4.5	4.2	.73	.32	8.1	1.3	5.9	.18	4.6	0.020	0.5	9.00	MW	CG	Z
0.219	5.56	10353	.50	12.7	.177	4.5	4.6	.81	.27	7.0	1.3	5.7	.23	5.7	0.021	0.5	9.75	MW	C	BO
0.219	5.56	EE-24	.50	12.7	.175	4.4	7.7	1.3	.25	6.4	1.9	8.5	.15	3.9	0.022	0.6	7.00	SST	CG	N
0.219	5.56	KK-83	.50	12.7	.175	4.4	4.8	.84	.26	6.6	1.2	5.5	.24	6.1	0.022	0.6	10.0	SST	C	N
0.219	5.56	H-78	.50	12.7	.169	4.3	11	2.0	.24	6.0	2.7	12	.20	5.1	0.025	0.6	8.00	SST	C	N
0.219	5.56	Q-4	.50	12.7	.169	4.3	13	2.2	.28	7.0	3.5	16	.23	5.7	0.025	0.6	8.00	MW	C	N
0.219	5.56	S-858	.50	12.7	.165	4.2	15	2.7	.22	5.5	3.3	15	.25	6.3	0.027	0.7	8.25	SST	C	N
0.219	5.56	10828	.50	12.7	.161	4.1	30	5.2	.21	5.2	6.1	27	.23	5.9	0.029	0.7	7.00	MW	C	N
0.219	5.56	3837	.50	12.7	.139	3.5	214	37	.05	1.3	11	47	.24	6.1	0.040	1.0	5.00	SPR	C	Z
0.219	5.56	Z-82	.50	12.7	.139	3.5	128	22	.08	2.1	11	47	.28	7.1	0.040	1.0	7.00	SPR	CG	Z
0.219	5.56	LL-31	.50	12.7	.119	3.0	266	47	.05	1.3	13	59	.45	11.4	0.050	1.3	9.00	SPR	CG	N
0.219	5.56	B17-123	.53	13.5	.203	5.2	.10	.02	.46	12	.04	.20	.08	1.9	0.008	0.2	8.50	MW	C	N
0.219	5.56	10583	.53	13.5	.193	4.9	1.0	.18	.43	11	.45	2.0	.10	2.5	0.013	0.3	6.50	MW	C	N
0.219	5.56	RR-5	.53	13.5	.163	4.1	18	3.2	.20	5.1	3.7	16	.25	6.4	0.028	0.7	8.00	SST	C	N
0.219	5.56	B7-11	.53	13.5	.163	4.1	20	3.4	.28	7.2	5.5	25	.24	6.0	0.028	0.7	8.50	MW	CG	Z
0.219	5.56	BB-11	.53	13.5	.159	4.0	17	3.0	.20	5.1	3.4	15	.33	8.4	0.030	0.8	11.0	SST	CG	N
0.219	5.56	BB-95	.53	13.5	.155	3.9	22	3.9	.18	4.5	4.0	18	.35	8.9	0.032	0.8	11.0	SST	CG	N
0.219	5.56	B-81	.53	13.5	.155	3.9	41	7.2	.13	3.4	5.4	24	.22	5.7	0.032	0.8	7.00	SST	CG	N
0.219	5.56	MM-7	.53	13.5	.139	3.5	80	14	.13	3.3	11	47	.40	10.2	0.040	1.0	10.0	SPR	CG	N
0.219	5.56	B9-25	.56	14.3	.199	5.1	.16	.03	.43	11	.07	.31	.13	3.2	0.010	0.3	11.8	MW	C	N
0.219	5.56	A9-12	.56	14.3	.197	5.0	.17	.03	.40	10	.07	.31	.17	4.2	0.011	0.3	14.0	SST	C	N
0.219	5.56	EE-99	.56	14.3	.179	4.5	4.2	.73	.36	9.2	1.5	6.7	.20	5.1	0.020	0.5	9.00	MW	C	N
0.219	5.56	S-192	.56	14.3	.161	4.1	26	4.5	.16	4.0	4.1	18	.23	5.9	0.029	0.7	7.00	SST	C	N
0.219	5.56	S-1208	.56	14.3	.149	3.8	38	6.7	.18	4.5	6.8	30	.35	8.9	0.035	0.9	10.0	SST	CG	N
0.219	5.56	A10-14	.56	14.3	.147	3.7	66	11	.12	3.0	7.9	35	.32	8.2	0.036	0.9	8.00	SPR	C	N
0.219	5.56	11419	.56	14.3	.141	3.6	67	12	.14	3.5	9.3	41	.37	9.4	0.039	1.0	9.50	SST	CG	N
0.219	5.56	NN-70	.59	15.1	.179	4.5	4.9	.85	.41	10	2.0	8.9	.18	4.6	0.020	0.5	8.00	MW	C	N
0.219	5.56	Q-80	.59	15.1	.169	4.3	11	1.9	.36	9.2	4.0	18	.23	5.7	0.025	0.6	9.00	MW	CG	N
0.219	5.56	00-27	.59	15.1	.159	4.0	19	3.3	.24	6.0	4.5	20	.33	8.4	0.030	0.8	10.0	SST	C	N
0.219	5.56	A9-34	.59	15.1	.147	3.7	56	9.9	.14	3.5	7.9	35	.32	8.2	0.036	0.9	9.00	SPR	CG	N
0.219	5.56	H-5	.63	15.9	.189	4.8	.66	.12	.40	10	.26	1.2	.23	5.7	0.015	0.4	15.0	MW	CG	N
0.219	5.56	M-21	.63	15.9	.179	4.5	4.2	.73	.43	11	1.8	7.9	.20	5.1	0.020	0.5	9.00	MW	C	Z
0.219	5.56	Q-70	.63	15.9	.175	4.4	4.8	.84	.38	9.7	1.8	8.2	.24	6.1	0.022	0.6	10.0	SST	C	N
0.219	5.56	S-714	.63	15.9	.175	4.4	6.1	1.1	.31	7.9	1.9	8.5	.20	5.2	0.022	0.6	8.25	SST	C	N
0.219	5.56	2667	.63	15.9	.171	4.3	8.3	1.5	.37	9.3	3.0	14	.26	6.6	0.024	0.6	9.75	MW	C	Z
0.219	5.56	B14-1	.63	15.9	.171	4.3	13	2.3	.29	7.4	3.7	17	.19	4.9	0.024	0.6	7.00	MW	C	N
0.219	5.56	3790	.63	15.9	.169	4.3	7.7	1.3	.30	7.6	2.3	10	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.219	5.56	I-69	.63	15.9	.169	4.3	9.6	1.7	.38	9.5	3.6	16	.25	6.4	0.025	0.6	10.0	MW	CG	Z
0.219	5.56	EE-20	.63	15.9	.159	4.0	15	2.7	.27	6.7	4.1	18	.36	9.1	0.030	0.8	12.0	SST	CG	N
0.219	5.56	MM-19	.63	15.9	.159	4.0	22	3.8	.31	7.9	6.7	30	.30	7.6	0.030	0.8	10.0	MW	CG	Z
0.219	5.56	S-5	.63	15.9	.155	3.9	21	3.7	.23	5.7	4.7	21	.40	10.2	0.032	0.8	11.5	SST	C	N
0.219	5.56	GG-68	.63	15.9	.149	3.8	38	6.6	.18	4.6	6.8	30	.35	8.9	0.035	0.9	10.0	SST	CG	N
0.219	5.56	EE-35	.63	15.9	.119	3.0	310	54	.06	1.5	19	82	.40	10.2	0.050	1.3	8.00	SPR	CG	N
0.219	5.56	AA-89	.66	16.7	.195	5.0	.27	.05	.49	12	.13	.59	.17	4.3	0.012	0.3	13.0	SST	C	N
0.219	5.56	MM-33	.66	16.7	.179	4.5	4.9	.85	.45	11	2.2	9.7	.16	4.1	0.020	0.5	8.00	MW	CG	N
0.219	5.56	B5-68	.66	16.7	.169	4.3	14	2.4	.19	4.9	2.7	12	.20	5.1	0.025	0.6	7.00	SST	C	N
0.219	5.56	2912	.66	16.7	.167	4.2	12	2.0	.38	9.7	4.4	20	.26	6.5	0.026	0.7	9.88	MW	CG	Z
0.219	5.56	2882	.66	16.7	.159	4.0	27	4.6	.25	6.5	6.7	30	.29	7.2	0.030	0.8	8.50	MW	C	N
0.219	5.56	S-946	.66	16.7	.157	4.0	27	4.7	.19	4.7	5.0	22	.29	7.5	0.031	0.8	8.50	SST	C	N
0.219	5.56	A-93	.66	16.7	.149	3.8	33	5.8	.22	5.5	7.2	32	.44	11.1	0.035	0.9	12.5	SPR	CG	N
0.219	5.56	NN-69	.69	17.4	.193	4.9	.37	.07	.51	13	.19	.83	.18	4.6	0.013	0.3	13.0	SST	C	N
0.219	5.56	I-78	.69	17.4	.191	4.9	.24	.04	.32	8.2	.08	.35	.36	9.2	0.014	0.4	25.0	SST	C	N
0.219	5.56	BB-46	.69	17.4	.189	4.8	1.2	.21	.54	14	.66	2.9	.15	3.8	0.015	0.4	9.00	MW	C	GI
0.219	5.56	EE-46	.69	17.4	.187	4.7	1.1	.19	.50	13	.54	2.4	.19	4.9	0.016	0.4	11.0	SST	C	N
0.219	5.56	LL-86	.69	17.4	.183	4.6	1.3	.24	.42	11	.56	2.5	.27	6.9	0.018	0.5	14.0	SST	C	N
0.219	5.56	B8-13	.69	17.4	.147	3.7	36	6.3	.22	5.6	7.8	35	.47	11.9	0.036	0.9	13.0	SPR	CG	N
0.219	5.56	J-18	.69	17.4	.139	3.5	71	12	.15	3.8	11	47	.44	11.2	0.040	1.0	11.0	SPR	CG	GI
0.219	5.56	NN-31	.69	17.4	.125	3.2	230	40	.07	1.9	17	74	.42	10.7	0.047	1.2	8.00	SPR	C	N
0.219																				



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEF.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.219	5.56	HH-43	.75	19.1	.159	4.0	19	3.4	.35	8.9	6.7	30	.33	8.4	0.030	0.8	11.0	MW	CG	N
0.219	5.56	TT-39	.75	19.1	.159	4.0	18	3.1	.26	6.5	4.5	20	.35	8.8	0.030	0.8	10.5	SST	C	N
0.219	5.56	11303	.75	19.1	.149	3.8	35	6.1	.19	4.9	6.8	30	.41	10.4	0.035	0.9	10.8	SST	C	N
0.219	5.56	A9-5	.78	19.8	.155	3.9	23	4.0	.35	9.0	8.1	36	.38	9.8	0.032	0.8	12.0	MW	CG	N
0.219	5.56	S-874	.78	19.8	.143	3.6	49	8.6	.18	4.5	8.6	38	.42	10.6	0.038	1.0	11.0	SST	CG	N
0.219	5.56	HH-16	.78	19.8	.099	2.5	514	90	.06	1.4	28	127	.60	15.2	0.060	1.5	10.0	SST	CG	N
0.219	5.56	V-61	.81	20.6	.179	4.5	2.8	.49	.51	13	1.4	6.4	.24	6.1	0.020	0.5	11.0	SST	C	N
0.219	5.56	MM-81	.81	20.6	.155	3.9	16	2.9	.30	7.6	4.9	22	.51	13.0	0.032	0.8	16.0	HD	CG	Z
0.219	5.56	Z-85	.81	20.6	.151	3.8	23	4.1	.30	7.6	7.0	31	.51	13.0	0.034	0.9	15.0	SPR	CG	N
0.219	5.56	1503	.81	20.6	.149	3.8	51	9.0	.20	5.0	10	45	.34	8.7	0.035	0.9	8.75	MW	C	Z
0.219	5.56	S-1555	.81	20.6	.143	3.6	49	8.6	.18	4.5	8.6	38	.46	11.6	0.038	1.0	11.0	SST	C	N
0.219	5.56	VV-38	.81	20.6	.129	3.3	118	21	.13	3.2	15	66	.56	14.3	0.045	1.1	11.5	SPR	C	Z
0.219	5.56	H-48	.84	21.4	.165	4.2	15	2.7	.32	8.2	5.0	22	.24	6.2	0.027	0.7	9.00	MW	CG	Z
0.219	5.56	II-58	.84	21.4	.153	3.9	20	3.6	.31	8.0	6.4	28	.50	12.6	0.033	0.8	15.0	SPR	CG	Z
0.219	5.56	10733	.88	22.2	.193	4.9	.64	.11	.67	17	.43	1.9	.12	3.1	0.013	0.3	8.50	SST	C	N
0.219	5.56	B-15	.88	22.2	.185	4.7	.79	.14	.55	14	.44	1.9	.32	8.2	0.017	0.4	18.0	SST	C	N
0.219	5.56	DD-38	.88	22.2	.179	4.5	2.6	.45	.56	14	1.4	6.4	.26	6.6	0.020	0.5	12.0	SST	C	N
0.219	5.56	S-716	.88	22.2	.175	4.4	4.3	.75	.45	11	1.9	8.5	.26	6.7	0.022	0.6	11.0	SST	C	N
0.219	5.56	S-1169	.88	22.2	.171	4.3	8.6	1.5	.29	7.3	2.5	11	.23	5.8	0.024	0.6	8.50	SST	C	N
0.219	5.56	S-1079	.88	22.2	.169	4.3	5.6	.98	.48	12	2.7	12	.35	8.9	0.025	0.6	14.0	SST	CG	N
0.219	5.56	2771	.88	22.2	.167	4.2	18	3.2	.24	6.2	4.4	20	.21	5.3	0.026	0.7	7.00	MW	C	Z
0.219	5.56	2900	.88	22.2	.163	4.1	9.8	1.7	.46	12	4.4	20	.42	10.7	0.028	0.7	15.0	MW	CG	Z
0.219	5.56	V-59	.88	22.2	.161	4.1	11	1.9	.38	9.7	4.1	18	.41	10.3	0.029	0.7	14.0	SST	CG	N
0.219	5.56	2529	.88	22.2	.139	3.5	58	10	.25	6.4	15	65	.56	14.2	0.040	1.0	13.0	MW	C	Z
0.219	5.56	HH-52	.88	22.2	.139	3.5	53	9.4	.20	5.0	11	47	.56	14.2	0.040	1.0	14.0	SPR	CG	Z
0.219	5.56	2801	.91	23.0	.181	4.6	2.0	.36	.63	16	1.3	5.7	.28	7.0	0.019	0.5	13.5	MW	C	Z
0.219	5.56	Z-27	.91	23.0	.173	4.4	7.3	1.3	.30	7.6	2.2	9.7	.22	5.5	0.023	0.6	8.50	SST	C	N
0.219	5.56	AA-15	.94	23.8	.191	4.9	.44	.08	.72	18	.31	1.4	.22	5.6	0.014	0.4	14.8	SST	C	N
0.219	5.56	W-42	.94	23.8	.167	4.2	5.0	.87	.47	12	2.3	10	.47	11.9	0.026	0.7	18.0	SST	CG	N
0.219	5.56	G-58	.94	23.8	.157	4.0	14	2.4	.43	11	5.9	26	.51	13.0	0.031	0.8	16.5	MW	CG	N
0.219	5.56	J-70	.94	23.8	.157	4.0	13	2.3	.41	10	5.5	24	.53	13.4	0.031	0.8	17.0	MW	CG	GI
0.219	5.56	A9-52	.97	24.6	.173	4.4	4.4	.78	.49	12	2.2	9.7	.29	7.4	0.023	0.6	12.7	SST	CG	N
0.219	5.56	2627	.97	24.6	.161	4.1	11	1.9	.52	13	5.7	25	.45	11.4	0.029	0.7	15.5	MW	CG	Z
0.219	5.56	159-A	1.00	25.4	.187	4.7	1.6	.28	.70	18	1.1	5.0	.16	4.1	0.016	0.4	9.00	MW	C	Z
0.219	5.56	160-A	1.00	25.4	.183	4.6	2.4	.42	.66	17	1.6	7.1	.19	4.9	0.018	0.5	9.75	MW	C	Z
0.219	5.56	4299	1.00	25.4	.183	4.6	2.0	.34	.78	20	1.5	6.7	.23	5.7	0.018	0.5	11.5	MW	C	Z
0.219	5.56	O-101	1.00	25.4	.183	4.6	1.9	.33	.77	19	1.4	6.3	.23	5.9	0.018	0.5	12.0	MW	C	N
0.219	5.56	A-65	1.00	25.4	.181	4.6	.58	.10	.28	7.1	.16	.72	.72	18.3	0.019	0.5	37.0	SST	C	N
0.219	5.56	351-A	1.00	25.4	.179	4.5	3.3	.58	.65	17	2.2	9.7	.24	6.0	0.020	0.5	10.8	MW	C	Z
0.219	5.56	12453	1.00	25.4	.175	4.4	3.7	.66	.68	17	2.5	11	.32	8.2	0.022	0.6	13.8	MW	C	Z
0.219	5.56	161-A	1.00	25.4	.173	4.4	5.5	.96	.60	15	3.3	15	.29	7.4	0.023	0.6	11.8	MW	C	N
0.219	5.56	K-39	1.00	25.4	.171	4.3	5.1	.89	.49	12	2.5	11	.34	8.5	0.024	0.6	13.0	SST	C	N
0.219	5.56	RR-39	1.00	25.4	.169	4.3	7.7	1.3	.51	13	4.0	18	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.219	5.56	2675	1.00	25.4	.167	4.2	6.3	1.1	.55	14	3.4	15	.46	11.6	0.026	0.7	16.5	MW	C	Z
0.219	5.56	O-46	1.00	25.4	.165	4.2	8.6	1.5	.57	15	5.0	22	.42	10.6	0.027	0.7	14.5	MW	C	Z
0.219	5.56	162-A	1.00	25.4	.163	4.1	11	2.0	.49	12	5.5	25	.40	10.1	0.028	0.7	13.3	MW	C	Z
0.219	5.56	A10-32	1.00	25.4	.149	3.8	27	4.7	.27	6.9	7.2	32	.53	13.3	0.035	0.9	15.0	SPR	CG	N
0.219	5.56	Z-89	1.06	27.0	.183	4.6	.48	.08	.40	10	.19	.84	.67	16.9	0.018	0.5	36.0	SST	C	N
0.219	5.56	J-2	1.06	27.0	.165	4.2	9.8	1.7	.51	13	5.0	22	.35	8.9	0.027	0.7	13.0	MW	CG	GI
0.219	5.56	KK-94	1.06	27.0	.151	3.8	22	3.8	.32	8.2	7.0	31	.58	14.7	0.034	0.9	16.0	SPR	C	N
0.219	5.56	B15-13	1.09	27.8	.141	3.6	36	6.2	.28	7.0	9.9	44	.70	17.8	0.039	1.0	18.0	SPR	CG	N
0.219	5.56	S-1054	1.13	28.6	.163	4.1	10	1.8	.37	9.4	3.7	16	.39	10.0	0.028	0.7	13.0	SST	C	N
0.219	5.56	FF-19	1.13	28.6	.159	4.0	9.6	1.7	.47	12	4.5	20	.54	13.7	0.030	0.8	18.0	SST	CG	N
0.219	5.56	Z-40	1.16	29.4	.159	4.0	17	3.0	.39	9.9	6.7	30	.56	9.1	0.030	0.8	12.0	MW	CG	N
0.219	5.56	2618	1.16	29.4	.147	3.7	26	4.6	.41	11	11	48	.65	16.5	0.036	0.9	17.0	MW	C	Z
0.219	5.56	10574	1.19	30.2	.171	4.3	4.0	.70	.76	19	3.0	14	.43	11.0	0.024	0.6	18.0	MW	CG	N
0.219	5.56	10065	1.25	31.8	.183	4.6	1.7	.30	.94	24	1.6	7.1	.25	6.4	0.018	0.5	13.0	MW	C	Z
0.219	5.56	11399	1.25	31.8	.179	4.5	2.5	.44	.86	22	2.2	9.7	.29	7.4	0.020	0.5	13.5	MW	C	Z
0.219	5.56	2861	1.25	31.8	.171	4.3	3.1	.54	.67	17	2.1	9.2	.58	14.6	0.024	0.6	23.0	MW	C	GI
0.219	5.56	S-145	1.25	31.8	.171	4.3	3.6	.63	.69	17	2.5	11	.44	11.3	0.024	0.6	17.5	SST	C	N
0.219	5.56	3779	1.25	31.8	.163	4.1	10	1.8	.54	14	5.5	25	.43	11.0	0.028	0.7	14.5	MW	C	Z
0.219	5.56	U-20	1.25	31.8	.141	3.6	38	6.7	.26	6.6	9.9	44	.70	17.8	0.039	1.0	17.0	SPR	C	N
0.219	5.56	A10-48	1.28	32.5	.181	4.6	1.0	.18	.84	21	.86	3.8	.44	11.3	0.019	0.5	22.3	SST	C	N
0.219	5.56	FF-91	1.31	33.3	.175	4.4	3.2	.56	.60	15	1.9	8.5	.33	8.4	0.022	0.6	14.0	SST	C	N
0.219	5.56	O-84	1.31	33.3	.163	4.1	9.9	1.7	.55	14	5.5	25	.44	11.2	0.028	0.7	14.8	MW	C	Z
0.219	5.56	S-891	1.38	34.9	.191	4.9	.43	.08	1.2	29	.49	2.2	.22	5.7	0.014	0.4	15.0	SST	C	N
0.219	5.56	159-B	1.38	34.9	.187	4.7	1.2	.20	.97	25	1.1	5.0	.20	5.2	0.016	0.4	11.8	MW	C	Z
0.219	5.56	160-B	1.38	34.9	.183	4.6	1.7	.30	.92	23	1.6	7.1	.25	6.3	0.018	0.5	12.8	MW	C	Z
0.219	5.56	1699	1.38	34.9	.179	4.5	1.5	.27	.94	24	1.4	6.4	.44	11.2	0.020	0.5	21.0	MW	C	Z
0.219	5.56																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.234	5.94	B17-127	.50	12.7	.178	4.5	19	3.3	.27	6.9	5.2	23	.21	5.2	0.028	0.7	7.33	MW	CG	Z
0.234	5.94	K-9	.50	12.7	.176	4.5	20	3.4	.27	6.8	5.3	23	.23	5.9	0.029	0.7	8.00	MW	CG	N
0.234	5.94	JJ-58	.50	12.7	.174	4.4	22	3.8	.20	5.0	4.3	19	.26	6.5	0.030	0.8	7.50	SST	C	N
0.234	5.94	S-1692	.50	12.7	.170	4.3	32	5.6	.16	4.1	5.1	23	.26	6.5	0.032	0.8	7.00	SST	C	N
0.234	5.94	IL-18	.50	12.7	.170	4.3	32	5.6	.22	5.6	7.0	31	.28	7.1	0.032	0.8	7.75	MW	C	N
0.234	5.94	S-3003	.50	12.7	.168	4.3	46	8.0	.12	3.1	5.6	25	.23	5.9	0.033	0.8	6.00	SST	C	N
0.234	5.94	A12-42	.50	12.7	.156	4.0	80	14	.11	2.8	8.7	39	.27	6.9	0.039	1.0	7.00	SST	CG	N
0.234	5.94	B-28	.50	12.7	.152	3.9	141	25	.08	1.9	11	48	.25	6.2	0.041	1.0	6.00	SPR	CG	GI
0.234	5.94	3518	.50	12.7	.150	3.8	253	44	.05	1.2	12	51	.19	4.8	0.042	1.1	4.50	SPR	CG	N
0.234	5.94	A13-13	.50	12.7	.150	3.8	112	20	.10	2.4	11	48	.29	7.5	0.042	1.1	7.00	SST	CG	N
0.234	5.94	Y-98	.50	12.7	.144	3.7	175	31	.08	2.0	14	62	.32	8.0	0.045	1.1	7.00	SPR	CG	Z
0.234	5.94	1505	.50	12.7	.140	3.6	268	47	.06	1.5	16	71	.28	7.2	0.047	1.2	6.00	HD	CG	Z
0.234	5.94	DD-39	.50	12.7	.134	3.4	481	84	.04	.93	18	78	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.234	5.94	2963	.53	13.5	.212	5.4	.63	.11	.47	12	.29	1.3	.07	1.7	0.011	0.3	5.00	MW	C	GI
0.234	5.94	FF-71	.53	13.5	.206	5.2	.77	.13	.41	10	.31	1.4	.13	3.2	0.014	0.4	8.00	SST	C	N
0.234	5.94	A10-8	.53	13.5	.196	5.0	3.4	.60	.37	9.4	1.3	5.6	.16	4.1	0.019	0.5	7.50	MW	C	N
0.234	5.94	S-1461	.53	13.5	.192	4.9	2.6	.46	.29	7.4	.77	3.4	.24	6.1	0.021	0.5	11.5	SST	CG	N
0.234	5.94	11216	.53	13.5	.190	4.8	7.8	1.4	.23	5.8	1.8	8.0	.13	3.4	0.022	0.6	6.00	SST	CG	N
0.234	5.94	3529	.53	13.5	.164	4.2	68	12	.14	3.5	9.5	42	.21	5.3	0.035	0.9	6.00	MW	CG	Z
0.234	5.94	M-102	.53	13.5	.160	4.1	45	7.8	.17	4.3	7.5	33	.33	8.5	0.037	0.9	9.00	SST	CG	N
0.234	5.94	CC-65	.53	13.5	.154	3.9	64	11	.15	3.7	9.4	42	.36	9.1	0.040	1.0	9.00	SST	CG	N
0.234	5.94	HH-47	.56	14.3	.202	5.1	.61	.11	.31	7.8	.19	.83	.26	6.5	0.016	0.4	15.0	SST	C	N
0.234	5.94	10930	.56	14.3	.198	5.0	2.2	.39	.40	10	.89	3.9	.16	4.1	0.018	0.5	8.00	SST	C	N
0.234	5.94	LL-98	.56	14.3	.192	4.9	8.4	1.5	.19	4.8	1.6	7.0	.13	3.2	0.021	0.5	5.00	SST	C	N
0.234	5.94	A-85	.56	14.3	.188	4.8	7.1	1.2	.38	9.6	2.7	12	.18	4.7	0.023	0.6	8.00	MW	C	Z
0.234	5.94	B1-13	.56	14.3	.182	4.6	14	2.4	.21	5.2	2.8	12	.18	4.5	0.026	0.7	6.75	SST	CG	N
0.234	5.94	IL-13	.56	14.3	.180	4.6	18	3.2	.26	6.5	4.7	21	.21	5.3	0.027	0.7	6.75	MW	C	N
0.234	5.94	A10-12	.56	14.3	.178	4.5	14	2.4	.32	8.2	4.5	20	.24	6.0	0.028	0.7	8.50	MW	CG	N
0.234	5.94	W-63	.56	14.3	.170	4.3	27	4.6	.19	4.9	5.1	23	.26	6.5	0.032	0.8	8.00	SST	CG	N
0.234	5.94	3216	.56	14.3	.166	4.2	40	7.0	.16	4.2	6.6	29	.27	6.9	0.034	0.9	8.00	SPR	CG	GI
0.234	5.94	S-832	.56	14.3	.166	4.2	35	6.1	.18	4.5	6.1	27	.27	6.9	0.034	0.9	8.00	SST	CG	N
0.234	5.94	S-929	.56	14.3	.164	4.2	60	10	.11	2.7	6.4	28	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.234	5.94	12031	.59	15.1	.208	5.3	.76	.13	.49	12	.37	1.7	.10	2.6	0.013	0.3	7.00	MW	C	N
0.234	5.94	JJ-67	.59	15.1	.190	4.8	7.4	1.3	.36	9.2	2.7	12	.17	4.3	0.022	0.6	6.75	MW	C	N
0.234	5.94	M-81	.59	15.1	.170	4.3	41	7.1	.14	3.4	5.5	25	.24	6.1	0.032	0.8	6.50	SPR	C	N
0.234	5.94	Z-19	.59	15.1	.156	4.0	52	9.1	.17	4.3	8.7	39	.37	9.4	0.039	1.0	9.50	SST	CG	N
0.234	5.94	W-96	.59	15.1	.126	3.2	304	53	.07	1.7	21	91	.43	11.0	0.054	1.4	8.00	SST	CG	N
0.234	5.94	B2-26	.59	15.1	.144	3.7	159	28	.09	2.2	14	62	.34	8.6	0.045	1.1	7.50	SPR	CG	N
0.234	5.94	CC-14	.63	15.9	.214	5.4	.11	.02	.50	13	.06	.24	.13	3.3	0.010	0.3	12.0	SST	C	N
0.234	5.94	IL-95	.63	15.9	.194	4.9	2.1	.38	.38	9.5	.81	3.6	.25	6.4	0.020	0.5	11.5	SST	C	N
0.234	5.94	PP-2	.63	15.9	.194	4.9	3.0	.52	.45	11	1.3	5.9	.18	4.6	0.020	0.5	9.00	SST	CG	N
0.234	5.94	A9-14	.63	15.9	.190	4.8	6.3	1.1	.29	7.3	1.8	8.0	.15	3.9	0.022	0.6	7.00	SST	CG	N
0.234	5.94	YY-20	.63	15.9	.190	4.8	3.7	.65	.35	8.9	1.3	5.8	.28	7.0	0.022	0.6	11.5	MW	C	N
0.234	5.94	FF-1	.63	15.9	.180	4.6	13	2.3	.35	8.9	4.7	21	.26	6.5	0.027	0.7	8.50	MW	C	N
0.234	5.94	VV-62	.63	15.9	.174	4.4	20	3.4	.32	8.2	6.3	28	.27	6.9	0.030	0.8	9.00	MW	CG	Z
0.234	5.94	B7-24	.63	15.9	.174	4.4	18	3.2	.34	8.6	6.2	28	.29	7.2	0.030	0.8	9.50	MW	CG	N
0.234	5.94	J-85	.63	15.9	.166	4.2	30	5.3	.22	5.6	6.6	29	.34	8.6	0.034	0.9	10.0	SPR	CG	N
0.234	5.94	11315	.63	15.9	.166	4.2	23	4.0	.21	5.3	4.8	21	.42	10.6	0.034	0.9	11.3	SST	C	N
0.234	5.94	B-12	.63	15.9	.158	4.0	43	7.6	.19	4.8	8.1	36	.38	9.7	0.038	1.0	10.0	SST	CG	N
0.234	5.94	GG-4	.63	15.9	.154	3.9	63	11	.16	4.0	10	45	.40	10.2	0.040	1.0	10.0	SPR	CG	N
0.234	5.94	11260	.63	15.9	.150	3.8	126	22	.09	2.3	12	51	.34	8.5	0.042	1.1	7.00	SPR	C	Z
0.234	5.94	DD-10	.66	16.7	.194	4.9	2.9	.51	.44	11	1.3	5.7	.22	5.6	0.020	0.5	10.0	MW	C	N
0.234	5.94	W-77	.66	16.7	.182	4.6	9.2	1.6	.30	7.7	2.8	12	.26	6.6	0.026	0.7	9.00	SST	C	N
0.234	5.94	I-92	.66	16.7	.174	4.4	20	3.4	.32	8.2	6.3	28	.27	6.9	0.030	0.8	9.00	MW	CG	N
0.234	5.94	B5-27	.66	16.7	.168	4.3	30	5.3	.20	5.1	6.0	27	.30	7.5	0.033	0.8	9.00	SPR	CG	N
0.234	5.94	M-32	.66	16.7	.168	4.3	21	3.6	.27	6.9	5.6	25	.36	9.2	0.033	0.8	11.0	SST	CG	N
0.234	5.94	VV-2	.69	17.4	.194	4.9	1.7	.30	.39	9.8	.66	2.9	.30	7.6	0.020	0.5	14.0	SST	C	N
0.234	5.94	YY-63	.69	17.4	.188	4.8	4.3	.75	.39	9.9	1.7	7.4	.30	7.6	0.023	0.6	12.0	MW	C	Z
0.234	5.94	IL-87	.69	17.4	.186	4.7	4.3	.75	.36	9.2	1.5	6.9	.32	8.2	0.024	0.6	12.5	SST	C	N
0.234	5.94	B-65	.69	17.4	.182	4.6	11	1.9	.26	6.7	2.8	12	.23	5.9	0.026	0.7	8.00	SST	C	N
0.234	5.94	A14-14	.69	17.4	.180	4.6	14	2.5	.32	8.3	4.7	21	.22	5.5	0.027	0.7	8.00	MW	CG	GI
0.234	5.94	S-3134	.69	17.4	.174	4.4	18	3.2	.23	5.9	4.3	19	.26	6.5	0.030	0.8	8.50	SST	CG	N
0.234	5.94	B2-24	.69	17.4	.158	4.0	50	8.7	.24	6.1	12	53	.42	10.6	0.038	1.0	10.0	MW	C	N
0.234	5.94	3632	.69	17.4	.154	3.9	63	11	.16	4.0	10	45	.44	11.2	0.040	1.0	10.0	SPR	C	Z
0.234	5.94	A14-53	.69	17.4	.150	3.8	77	14	.14	3.6	11	48	.39	9.9	0.042	1.1	9.25	SST	CG	N
0.234	5.94	Y-93	.69	17.4	.146	3.7	112	20	.12	3.0	13	59	.40	10.1	0.044	1.1	9.00	SPR	CG	Z
0.234	5.94	DD-75	.69	17.4	.134	3.4	288	51	.08	2.2	24	109	.35	8.9	0.050	1.3	7.00	MW	CG	N
0.234	5.94	10011	.69	17.5	.200	5.1	1.7	.29	.52	13	.87	3.9	.17	4.3	0.017	0.4	9.00	MW	C	Z
0.234	5.94	11163	.72	18.2	.214	5.4	.20	.03	.62	16	.12	.55	.10	2.4	0.010	0.3	8.50	MW	C	Z
0.234	5.94	B11-31	.72	18.2	.182	4.6	13	2.2	.33</											




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.234	5.94	S-88	1.28	32.5	.186	4.7	4.1	.71	.57	15	2.3	10	.34	8.5	0.024	0.6	13.0	SST	C	N
0.234	5.94	B9-41	1.31	33.3	.192	4.9	3.0	.53	.78	20	2.4	10	.24	6.1	0.021	0.5	11.5	MW	CG	Z
0.234	5.94	W-6	1.31	33.3	.176	4.5	5.4	.95	.67	17	3.6	16	.64	16.2	0.029	0.7	21.0	SST	C	N
0.234	5.94	B3-43	1.33	33.7	.180	4.6	5.1	.89	.79	20	4.0	18	.54	13.7	0.027	0.7	19.0	MW	C	BO
0.234	5.94	DD-46	1.44	36.5	.194	4.9	1.2	.20	1.0	26	1.2	5.2	.42	10.7	0.020	0.5	20.0	SST	C	N
0.234	5.94	S-1540	1.50	38.1	.206	5.2	.50	.09	.99	25	.50	2.2	.17	4.3	0.014	0.4	11.0	SST	C	N
0.234	5.94	QQ-47	1.50	38.1	.192	4.9	1.3	.23	1.0	26	1.4	6.1	.46	11.7	0.021	0.5	21.0	SST	C	N
0.234	5.94	S-224	1.50	38.1	.186	4.7	2.8	.50	.82	21	2.3	10	.45	11.4	0.024	0.6	17.8	SST	C	N
0.234	5.94	B5-26	1.50	38.1	.160	4.1	20	3.5	.40	10	8.0	36	.73	18.6	0.037	0.9	19.8	SPR	CG	N
0.234	5.94	CC-3	1.50	38.1	.154	3.9	30	5.2	.34	8.6	10	45	.80	20.3	0.040	1.0	19.0	SPR	C	N
0.234	5.94	L-51	1.69	42.8	.206	5.2	.13	.02	1.1	27	.14	.60	.62	15.6	0.014	0.4	43.0	MW	C	N
0.234	5.94	DD-95	1.81	46.0	.188	4.8	2.1	.36	.99	25	2.1	9.1	.48	12.3	0.023	0.6	20.0	SST	C	N
0.234	5.94	TT-68	1.88	47.6	.194	4.9	.97	.17	1.4	35	1.4	6.0	.48	12.2	0.020	0.5	23.0	SST	C	N
0.234	5.94	2804	2.00	50.8	.164	4.2	11	2.0	.83	21	9.5	42	.91	23.1	0.035	0.9	26.0	MW	CG	Z
0.234	5.94	3976	2.22	56.4	.132	3.4	68	12	.28	7.0	19	83	1.35	34.3	0.051	1.3	25.5	SPR	C	Z
0.234	5.94	0-51	2.25	57.2	.204	5.2	.29	.05	1.8	47	.53	2.4	.41	10.3	0.015	0.4	26.0	MW	C	N
0.234	5.94	10431	2.25	57.2	.172	4.4	7.2	1.3	.97	25	7.0	31	.78	19.7	0.031	0.8	24.0	MW	C	GI
0.234	5.94	3680	2.44	61.9	.182	4.6	4.6	.81	.90	23	4.2	19	.49	12.4	0.026	0.7	17.8	MW	C	Z
0.234	5.94	B4-21	2.50	63.5	.174	4.4	5.0	.88	1.3	32	6.3	28	.91	23.1	0.030	0.8	29.3	MW	C	N
0.234	5.94	2653	2.53	64.3	.164	4.2	14	2.5	.49	12	6.8	30	.75	19.1	0.035	0.9	21.5	SPR	CG	Z
0.234	5.94	B12-68	2.56	65.1	.184	4.7	2.4	.41	1.6	40	3.7	17	.73	18.4	0.025	0.6	28.0	MW	C	Z
0.234	5.94	0-42	2.75	69.9	.150	3.8	15	2.7	.71	18	11	48	1.60	40.5	0.042	1.1	38.0	SST	CG	N
0.234	5.94	11306	3.25	82.6	.184	4.7	1.1	.19	2.0	50	2.2	9.7	1.30	33.0	0.025	0.6	51.0	SST	C	N
0.234	5.94	B2-68	3.33	84.5	.158	4.0	8.9	1.6	.97	25	8.7	39	1.81	45.8	0.038	1.0	46.5	SPR	CL	N
0.234	5.94	3636	4.50	114.3	.162	4.1	6.1	1.1	1.7	43	10	46	1.94	49.4	0.036	0.9	53.0	MW	C	Z
0.234	5.94	12738	7.25	184.2	.156	4.0	9.3	1.6	1.0	25	9.3	42	1.99	50.5	0.039	1.0	50.0	SPR	C	N
0.240	6.10	70520	.25	6.4	.208	5.3	6.2	1.1	.17	4.2	1.0	4.6	.05	1.4	0.016	0.4	3.38	MW	CG	N
0.240	6.10	70520S	.25	6.4	.208	5.3	5.3	.92	.13	3.3	.68	3.0	.05	1.4	0.016	0.4	3.38	SST	CG	N
0.240	6.10	70536	.25	6.4	.204	5.2	9.5	1.7	.15	3.9	1.5	6.5	.06	1.6	0.018	0.5	3.50	MW	CG	N
0.240	6.10	70536S	.25	6.4	.204	5.2	8.0	1.4	.12	3.1	.97	4.3	.06	1.6	0.018	0.5	3.50	SST	CG	N
0.240	6.10	70553	.25	6.4	.200	5.1	13	2.2	.16	4.0	2.0	8.9	.08	1.9	0.020	0.5	3.75	MW	CG	N
0.240	6.10	70553S	.25	6.4	.200	5.1	11	1.9	.12	3.2	1.3	5.9	.08	1.9	0.020	0.5	3.75	SST	CG	N
0.240	6.10	70577	.25	6.4	.196	5.0	19	3.3	.14	3.6	2.6	12	.08	2.1	0.022	0.6	3.75	MW	CG	N
0.240	6.10	70577S	.25	6.4	.196	5.0	16	2.8	.11	2.8	1.8	7.8	.08	2.1	0.022	0.6	3.75	SST	CG	N
0.240	6.10	70521	.31	7.9	.208	5.3	4.8	.84	.21	5.4	1.0	4.6	.06	1.5	0.016	0.4	3.75	MW	CG	N
0.240	6.10	70521S	.31	7.9	.208	5.3	4.1	.71	.17	4.3	.68	3.0	.06	1.5	0.016	0.4	3.75	SST	CG	N
0.240	6.10	70537	.31	7.9	.204	5.2	7.4	1.3	.20	5.0	1.5	6.5	.07	1.8	0.018	0.5	3.88	MW	CG	N
0.240	6.10	70537S	.31	7.9	.204	5.2	6.2	1.1	.16	3.9	.97	4.3	.07	1.8	0.018	0.5	3.88	SST	CG	N
0.240	6.10	70554	.31	7.9	.200	5.1	9.8	1.7	.20	5.2	2.0	8.9	.09	2.2	0.020	0.5	4.25	MW	CG	N
0.240	6.10	70554S	.31	7.9	.200	5.1	8.3	1.5	.16	4.0	1.3	5.9	.09	2.2	0.020	0.5	4.25	SST	CG	N
0.240	6.10	70578	.31	7.9	.196	5.0	15	2.6	.18	4.6	2.6	12	.09	2.4	0.022	0.6	4.25	MW	CG	N
0.240	6.10	70578S	.31	7.9	.196	5.0	12	2.2	.14	3.6	1.8	7.8	.09	2.4	0.022	0.6	4.25	SST	CG	N
0.240	6.10	70620	.31	7.9	.188	4.8	28	4.9	.14	3.7	4.1	18	.11	2.9	0.026	0.7	4.38	MW	CG	N
0.240	6.10	70620S	.31	7.9	.188	4.8	24	4.2	.11	2.9	2.7	12	.11	2.9	0.026	0.7	4.38	SST	CG	N
0.240	6.10	70642	.31	7.9	.182	4.6	40	7.0	.14	3.6	5.6	25	.14	3.5	0.029	0.7	4.75	MW	CG	N
0.240	6.10	70642S	.31	7.9	.182	4.6	34	6.0	.11	2.8	3.8	17	.14	3.5	0.029	0.7	4.75	SST	CG	N
0.240	6.10	70660	.31	7.9	.176	4.5	63	11	.12	3.0	7.5	33	.15	3.8	0.032	0.8	4.63	MW	CG	N
0.240	6.10	70660S	.31	7.9	.176	4.5	53	9.4	.09	2.4	5.0	22	.15	3.8	0.032	0.8	4.63	SST	CG	N
0.240	6.10	70679	.31	7.9	.170	4.3	88	15	.10	2.7	9.2	41	.17	4.3	0.035	0.9	4.88	MW	CG	N
0.240	6.10	70679S	.31	7.9	.170	4.3	75	13	.08	2.1	6.3	28	.17	4.3	0.035	0.9	4.88	SST	CG	N
0.240	6.10	70700	.31	7.9	.164	4.2	127	22	.09	2.3	12	52	.19	4.7	0.038	1.0	4.88	MW	CG	N
0.240	6.10	70700S	.31	7.9	.164	4.2	108	19	.07	1.9	7.9	35	.19	4.7	0.038	1.0	4.88	SST	CG	N
0.240	6.10	70720	.31	7.9	.160	4.1	155	27	.09	2.2	14	60	.20	5.1	0.040	1.0	5.00	MW	CG	N
0.240	6.10	70720S	.31	7.9	.160	4.1	132	23	.07	1.8	9.2	41	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.240	6.10	12732	.38	9.5	.204	5.2	8.7	1.5	.11	2.8	.97	4.3	.06	1.5	0.018	0.5	3.38	SST	CG	N
0.240	6.10	70522	.38	9.7	.208	5.3	3.9	.68	.26	6.7	1.0	4.6	.07	1.7	0.016	0.4	4.13	MW	CG	N
0.240	6.10	70522S	.38	9.7	.208	5.3	3.3	.58	.21	5.2	.68	3.0	.07	1.7	0.016	0.4	4.13	SST	CG	N
0.240	6.10	70538	.38	9.7	.204	5.2	5.9	1.0	.25	6.3	1.5	6.5	.08	2.0	0.018	0.5	4.38	MW	CG	N
0.240	6.10	70538S	.38	9.7	.204	5.2	5.0	.88	.19	4.9	.97	4.3	.08	2.0	0.018	0.5	4.38	SST	CG	N
0.240	6.10	70555	.38	9.7	.200	5.1	7.7	1.4	.26	6.6	2.0	8.9	.10	2.4	0.020	0.5	4.75	MW	CG	N
0.240	6.10	70555S	.38	9.7	.200	5.1	6.6	1.1	.20	5.1	1.3	5.9	.10	2.4	0.020	0.5	4.75	SST	CG	N
0.240	6.10	70579	.38	9.7	.196	5.0	12	2.1	.22	5.5	2.6	12	.10	2.6	0.022	0.6	4.63	MW	CG	N
0.240	6.10	70579S	.38	9.7	.196	5.0	10	1.8	.17	4.3	1.8	7.8	.10	2.6	0.022	0.6	4.63	SST	CG	N
0.240	6.10	70600	.38	9.7	.192	4.9	17	2.9	.21	5.2	3.4	15	.12	3.0	0.024	0.6	4.88	MW	CG	N
0.240	6.10	70600S	.38	9.7	.192	4.9	14	2.5	.16	4.1	2.3	10	.12	3.0	0.024	0.6	4.88	SST	CG	N
0.240	6.10	70621	.38	9.7	.188	4.8	24	4.1	.17	4.4	4.1	18	.13	3.2	0.026	0.7	4.88	MW	CG	N
0.240	6.10	70621S	.38	9.7	.188	4.8	20	3.5	.14	3.4	2.7	12	.13	3.2	0.026	0.7	4.88	SST	CG	N
0.240	6.10	70643	.38	9.7	.182	4.6	33	5.7	.17	4.4	5.6	25	.15	3.9	0.029	0.7	5.25	MW	CG	N
0.240	6.10	70643S	.38	9.7	.182	4.6	28	4.9	.14	3.4	3.8	17	.15	3						



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	B3-61	.59	15.1	.150	3.8	159	28	.12	3.0	19	85	.32	8.0	0.045	1.1	7.00	MW	CG	N
0.240	6.10	70526	.63	16.0	.208	5.3	2.3	.40	.45	11	1.0	4.6	.09	2.3	0.016	0.4	5.63	MW	CG	N
0.240	6.10	70526S	.63	16.0	.208	5.3	2.0	.34	.35	8.9	.68	3.0	.09	2.3	0.016	0.4	5.63	SST	CG	N
0.240	6.10	70542	.63	16.0	.204	5.2	3.5	.60	.42	11	1.5	6.5	.11	2.7	0.018	0.5	6.00	MW	CG	N
0.240	6.10	70542S	.63	16.0	.204	5.2	2.9	.51	.33	8.4	.97	4.3	.11	2.7	0.018	0.5	6.00	SST	CG	N
0.240	6.10	70560	.63	16.0	.200	5.1	5.1	.89	.39	9.9	2.0	8.9	.13	3.2	0.020	0.5	6.25	MW	CG	N
0.240	6.10	70560S	.63	16.0	.200	5.1	4.3	.76	.31	7.8	1.3	5.9	.13	3.2	0.020	0.5	6.25	SST	CG	N
0.240	6.10	70561	.63	16.0	.200	5.1	3.3	.58	.46	12	1.5	6.8	.17	4.3	0.020	0.5	8.50	MW	CG	N
0.240	6.10	70561S	.63	16.0	.200	5.1	2.8	.49	.46	12	1.3	5.7	.17	4.3	0.020	0.5	8.50	SST	CG	N
0.240	6.10	70583	.63	16.0	.196	5.0	6.9	1.2	.38	9.7	2.6	12	.15	3.8	0.022	0.6	6.75	MW	CG	N
0.240	6.10	70583S	.63	16.0	.196	5.0	5.9	1.0	.30	7.6	1.8	7.8	.15	3.8	0.022	0.6	6.75	SST	CG	N
0.240	6.10	70604	.63	16.0	.192	4.9	9.6	1.7	.36	9.1	3.4	15	.17	4.3	0.024	0.6	7.00	MW	CG	N
0.240	6.10	70604S	.63	16.0	.192	4.9	8.1	1.4	.28	7.1	2.3	10	.17	4.3	0.024	0.6	7.00	SST	CG	N
0.240	6.10	70625	.63	16.0	.188	4.8	13	2.2	.32	8.2	4.1	18	.19	4.9	0.026	0.7	7.38	MW	CG	N
0.240	6.10	70625S	.63	16.0	.188	4.8	11	1.9	.25	6.5	2.7	12	.19	4.9	0.026	0.7	7.38	SST	CG	N
0.240	6.10	70647	.63	16.0	.182	4.6	18	3.2	.30	7.7	5.6	25	.23	5.8	0.029	0.7	7.88	MW	CG	N
0.240	6.10	70647S	.63	16.0	.182	4.6	16	2.7	.24	6.1	3.8	17	.23	5.8	0.029	0.7	7.88	SST	CG	N
0.240	6.10	70665	.63	16.0	.176	4.5	28	4.9	.27	6.8	7.5	33	.26	6.5	0.032	0.8	8.00	MW	CG	N
0.240	6.10	70665S	.63	16.0	.176	4.5	24	4.2	.21	5.3	5.0	22	.26	6.5	0.032	0.8	8.00	SST	CG	N
0.240	6.10	70684	.63	16.0	.170	4.3	39	6.8	.24	6.0	9.2	41	.29	7.4	0.035	0.9	8.38	MW	CG	N
0.240	6.10	70684S	.63	16.0	.170	4.3	33	5.8	.19	4.8	6.3	28	.29	7.4	0.035	0.9	8.38	SST	CG	N
0.240	6.10	70705	.63	16.0	.164	4.2	57	9.9	.21	5.3	12	52	.32	8.1	0.038	1.0	8.38	MW	CG	N
0.240	6.10	70705S	.63	16.0	.164	4.2	48	8.4	.16	4.2	7.9	35	.32	8.1	0.038	1.0	8.38	SST	CG	N
0.240	6.10	70725	.63	16.0	.160	4.1	67	12	.20	5.2	14	60	.36	9.0	0.040	1.0	8.88	MW	CG	N
0.240	6.10	70725S	.63	16.0	.160	4.1	57	9.9	.16	4.1	9.2	41	.36	9.0	0.040	1.0	8.88	SST	CG	N
0.240	6.10	70746	.63	16.0	.156	4.0	85	15	.18	4.7	16	70	.37	9.3	0.042	1.1	8.75	MW	CG	N
0.240	6.10	70746S	.63	16.0	.156	4.0	72	13	.15	3.7	11	47	.37	9.3	0.042	1.1	8.75	SST	CG	N
0.240	6.10	70765	.63	16.0	.150	3.8	115	20	.17	4.2	19	85	.40	10.1	0.045	1.1	8.88	MW	CG	N
0.240	6.10	70765S	.63	16.0	.150	3.8	98	17	.13	3.3	13	57	.40	10.1	0.045	1.1	8.88	SST	CG	N
0.240	6.10	70527	.69	17.5	.208	5.3	2.0	.35	.51	13	1.0	4.6	.10	2.5	0.016	0.4	6.25	MW	CG	N
0.240	6.10	70527S	.69	17.5	.208	5.3	1.7	.30	.40	10	.68	3.0	.10	2.5	0.016	0.4	6.25	SST	CG	N
0.240	6.10	70543	.69	17.5	.204	5.2	3.1	.54	.47	12	1.5	6.5	.12	3.0	0.018	0.5	6.50	MW	CG	N
0.240	6.10	70543S	.69	17.5	.204	5.2	2.6	.46	.37	9.4	.97	4.3	.12	3.0	0.018	0.5	6.50	SST	CG	N
0.240	6.10	70562	.69	17.5	.200	5.1	4.1	.71	.49	13	2.0	8.9	.15	3.7	0.020	0.5	7.38	MW	CG	N
0.240	6.10	70562S	.69	17.5	.200	5.1	3.4	.60	.39	9.8	1.3	5.9	.15	3.7	0.020	0.5	7.38	SST	CG	N
0.240	6.10	70584	.69	17.5	.196	5.0	6.1	1.1	.43	11	2.6	12	.16	4.1	0.022	0.6	7.38	MW	CG	N
0.240	6.10	70584S	.69	17.5	.196	5.0	5.2	.91	.34	8.6	1.8	7.8	.16	4.1	0.022	0.6	7.38	SST	CG	N
0.240	6.10	70605	.69	17.5	.192	4.9	8.7	1.5	.39	10	3.4	15	.18	4.6	0.024	0.6	7.50	MW	CG	N
0.240	6.10	70605S	.69	17.5	.192	4.9	7.4	1.3	.31	7.8	2.3	10	.18	4.6	0.024	0.6	7.50	SST	CG	N
0.240	6.10	70626	.69	17.5	.188	4.8	11	1.9	.37	9.4	4.1	18	.21	5.4	0.026	0.7	8.13	MW	CG	N
0.240	6.10	70626S	.69	17.5	.188	4.8	9.4	1.6	.29	7.4	2.7	12	.21	5.4	0.026	0.7	8.13	SST	CG	N
0.240	6.10	70648	.69	17.5	.182	4.6	17	2.9	.34	8.6	5.6	25	.25	6.3	0.029	0.7	8.50	MW	CG	N
0.240	6.10	70648S	.69	17.5	.182	4.6	14	2.5	.27	6.8	3.8	17	.25	6.3	0.029	0.7	8.50	SST	CG	N
0.240	6.10	70666	.69	17.5	.176	4.5	25	4.4	.30	7.6	7.5	33	.28	7.1	0.032	0.8	8.75	MW	CG	N
0.240	6.10	70666S	.69	17.5	.176	4.5	21	3.7	.24	6.0	5.0	22	.28	7.1	0.032	0.8	8.75	SST	CG	N
0.240	6.10	70685	.69	17.5	.170	4.3	35	6.1	.27	6.7	9.2	41	.32	8.2	0.035	0.9	9.25	MW	CG	N
0.240	6.10	70685S	.69	17.5	.170	4.3	30	5.2	.21	5.4	6.3	28	.32	8.2	0.035	0.9	9.25	SST	CG	N
0.240	6.10	70706	.69	17.5	.164	4.2	51	8.9	.23	5.9	12	52	.35	8.8	0.038	1.0	9.13	MW	CG	N
0.240	6.10	70706S	.69	17.5	.164	4.2	43	7.6	.18	4.7	7.9	35	.35	8.8	0.038	1.0	9.13	SST	CG	N
0.240	6.10	70726	.69	17.5	.160	4.1	59	10	.23	5.8	14	60	.39	9.9	0.040	1.0	9.75	MW	CG	N
0.240	6.10	70726S	.69	17.5	.160	4.1	50	8.8	.18	4.6	9.2	41	.39	9.9	0.040	1.0	9.75	SST	CG	N
0.240	6.10	70747	.69	17.5	.156	4.0	75	13	.21	5.3	16	70	.40	10.3	0.042	1.1	9.63	MW	CG	N
0.240	6.10	70747S	.69	17.5	.156	4.0	64	11	.17	4.2	11	47	.40	10.3	0.042	1.1	9.63	SST	CG	N
0.240	6.10	70766	.69	17.5	.150	3.8	102	18	.19	4.7	19	85	.44	11.1	0.045	1.1	9.75	MW	CG	N
0.240	6.10	70766S	.69	17.5	.150	3.8	87	15	.15	3.8	13	57	.44	11.1	0.045	1.1	9.75	SST	CG	N
0.240	6.10	70528	.75	19.1	.208	5.3	1.9	.33	.54	14	1.0	4.6	.10	2.6	0.016	0.4	6.38	MW	CG	N
0.240	6.10	70528S	.75	19.1	.208	5.3	1.6	.28	.42	11	.68	3.0	.10	2.6	0.016	0.4	6.38	SST	CG	N
0.240	6.10	70544	.75	19.1	.204	5.2	2.8	.49	.52	13	1.5	6.5	.12	3.1	0.018	0.5	6.88	MW	CG	N
0.240	6.10	70544S	.75	19.1	.204	5.2	2.4	.42	.41	10	.97	4.3	.12	3.1	0.018	0.5	6.88	SST	CG	N
0.240	6.10	70563	.75	19.1	.200	5.1	3.7	.65	.54	14	2.0	8.9	.16	4.0	0.020	0.5	7.88	MW	CG	N
0.240	6.10	70563S	.75	19.1	.200	5.1	3.1	.55	.42	11	1.3	5.9	.16	4.0	0.020	0.5	7.88	SST	CG	N
0.240	6.10	70585	.75	19.1	.196	5.0	5.6	.97	.48	12	2.6	12	.17	4.4	0.022	0.6	7.88	MW	CG	N
0.240	6.10	70585S	.75	19.1	.196	5.0	4.7	.83	.37	9.5	1.8	7.8	.17	4.4	0.022	0.6	7.88	SST	CG	N
0.240	6.10	B4-35	.75	19.1	.196	5.0	4.7	.82	.37	9.5	1.8	7.8	.18	4.5	0.022	0.6	8.00	SST	CG	N
0.240	6.10	70606	.75	19.1	.192	4.9	7.8	1.4	.44	11	3.4	15	.20	5.0	0.024	0.6	8.13	MW	CG	N
0.240	6.10	70606S	.75	19.1	.192	4.9	6.6	1.2	.34	8.7	2.3	10	.20	5.0	0.024	0.6	8.13	SST	CG	N
0.240	6.10	70627	.75	19.1	.188	4.8	10	1.8	.41	10	4.1	18	.23	5.8	0.026	0.7	8.75	MW	CG	N
0.240	6.10	70627S	.75	19.1	.188	4.8	8.5	1.5	.32	8.2	2.7	12	.23	5.8	0.026	0.7	8.75	SST	CG	N
0.240	6.10	70649	.75	19.1	.182	4.6	15	2.7	.37	9.3	5.6	25	.26	6.7	0.029					




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70548	1.00	25.4	.204	5.2	2.1	.37	.70	18	1.5	6.5	.16	3.9	0.018	0.5	8.63	MW	CG	N
0.240	6.10	70548S	1.00	25.4	.204	5.2	1.8	.31	.54	14	.97	4.3	.16	3.9	0.018	0.5	8.63	SST	CG	N
0.240	6.10	70568	1.00	25.4	.200	5.1	2.8	.48	.73	18	2.0	8.9	.20	5.0	0.020	0.5	9.88	MW	CG	N
0.240	6.10	70568S	1.00	25.4	.200	5.1	2.3	.41	.57	14	1.3	5.9	.20	5.0	0.020	0.5	9.88	SST	CG	N
0.240	6.10	70591	1.00	25.4	.196	5.0	4.2	.74	.63	16	2.6	12	.21	5.4	0.022	0.6	9.75	MW	CG	N
0.240	6.10	70591S	1.00	25.4	.196	5.0	3.6	.63	.49	12	1.8	7.8	.21	5.4	0.022	0.6	9.75	SST	CG	N
0.240	6.10	70611	1.00	25.4	.192	4.9	5.8	1.0	.59	15	3.4	15	.25	6.2	0.024	0.6	10.3	MW	CG	N
0.240	6.10	70611S	1.00	25.4	.192	4.9	4.9	.86	.46	12	2.3	10	.25	6.2	0.024	0.6	10.3	SST	CG	N
0.240	6.10	70632	1.00	25.4	.188	4.8	7.4	1.3	.55	14	4.1	18	.29	7.3	0.026	0.7	11.0	MW	CG	N
0.240	6.10	70632S	1.00	25.4	.188	4.8	6.3	1.1	.43	11	2.7	12	.29	7.3	0.026	0.7	11.0	SST	CG	N
0.240	6.10	70653	1.00	25.4	.182	4.6	11	2.0	.50	13	5.6	25	.34	8.7	0.029	0.7	11.8	MW	CG	N
0.240	6.10	70653S	1.00	25.4	.182	4.6	9.5	1.7	.40	10	3.8	17	.34	8.7	0.029	0.7	11.8	SST	CG	N
0.240	6.10	70671	1.00	25.4	.176	4.5	16	2.8	.47	12	7.5	33	.40	10.2	0.032	0.8	12.5	MW	CG	N
0.240	6.10	70671S	1.00	25.4	.176	4.5	14	2.4	.37	9.4	5.0	22	.40	10.2	0.032	0.8	12.5	SST	CG	N
0.240	6.10	70690	1.00	25.4	.170	4.3	23	4.0	.41	10	9.2	41	.46	11.6	0.035	0.9	13.0	MW	CG	N
0.240	6.10	70690S	1.00	25.4	.170	4.3	19	3.4	.32	8.2	6.3	28	.46	11.6	0.035	0.9	13.0	SST	CG	N
0.240	6.10	70711	1.00	25.4	.164	4.2	33	5.7	.36	9.1	12	52	.50	12.7	0.038	1.0	13.1	MW	CG	N
0.240	6.10	70711S	1.00	25.4	.164	4.2	28	4.9	.29	7.3	7.9	35	.50	12.7	0.038	1.0	13.1	SST	CG	N
0.240	6.10	70731	1.00	25.4	.160	4.1	39	6.9	.35	8.8	14	60	.55	14.0	0.040	1.0	13.8	MW	CG	N
0.240	6.10	70731S	1.00	25.4	.160	4.1	33	5.8	.28	7.0	9.2	41	.55	14.0	0.040	1.0	13.8	SST	CG	N
0.240	6.10	70752	1.00	25.4	.156	4.0	48	8.4	.33	8.3	16	70	.59	14.9	0.042	1.1	14.0	MW	CG	N
0.240	6.10	70752S	1.00	25.4	.156	4.0	41	7.1	.26	6.6	11	47	.59	14.9	0.042	1.1	14.0	SST	CG	N
0.240	6.10	70771	1.00	25.4	.150	3.8	67	12	.28	7.2	19	85	.62	15.7	0.045	1.1	13.8	MW	CG	N
0.240	6.10	70771S	1.00	25.4	.150	3.8	57	10	.22	5.7	13	57	.62	15.7	0.045	1.1	13.8	SST	CG	N
0.240	6.10	70570	1.13	28.7	.200	5.1	2.7	.47	.74	19	2.0	8.9	.20	5.1	0.020	0.5	10.0	MW	CG	N
0.240	6.10	70570S	1.13	28.7	.200	5.1	2.3	.40	.58	15	1.3	5.9	.20	5.1	0.020	0.5	10.0	SST	CG	N
0.240	6.10	70593	1.13	28.7	.196	5.0	3.6	.63	.73	19	2.6	12	.24	6.1	0.022	0.6	11.0	MW	CG	N
0.240	6.10	70593S	1.13	28.7	.196	5.0	3.1	.54	.57	15	1.8	7.8	.24	6.1	0.022	0.6	11.0	SST	CG	N
0.240	6.10	70613	1.13	28.7	.192	4.9	4.9	.86	.70	18	3.4	15	.28	7.1	0.024	0.6	11.6	MW	CG	N
0.240	6.10	70613S	1.13	28.7	.192	4.9	4.2	.73	.55	14	2.3	10	.28	7.1	0.024	0.6	11.6	SST	CG	N
0.240	6.10	70634	1.13	28.7	.188	4.8	6.4	1.1	.64	16	4.1	18	.33	8.3	0.026	0.7	12.5	MW	CG	N
0.240	6.10	70634S	1.13	28.7	.188	4.8	5.4	.95	.50	13	2.7	12	.33	8.3	0.026	0.7	12.5	SST	CG	N
0.240	6.10	70654	1.13	28.7	.182	4.6	9.7	1.7	.58	15	5.6	25	.38	9.7	0.029	0.7	13.1	MW	CG	N
0.240	6.10	70654S	1.13	28.7	.182	4.6	8.2	1.4	.46	12	3.8	17	.38	9.7	0.029	0.7	13.1	SST	CG	N
0.240	6.10	70673	1.13	28.7	.176	4.5	14	2.5	.53	14	7.5	33	.45	11.4	0.032	0.8	14.0	MW	CG	N
0.240	6.10	70673S	1.13	28.7	.176	4.5	12	2.1	.42	11	5.0	22	.45	11.4	0.032	0.8	14.0	SST	CG	N
0.240	6.10	70692	1.13	28.7	.170	4.3	20	3.4	.47	12	9.2	41	.52	13.1	0.035	0.9	14.8	MW	CG	N
0.240	6.10	70692S	1.13	28.7	.170	4.3	17	2.9	.38	9.5	6.3	28	.52	13.1	0.035	0.9	14.8	SST	CG	N
0.240	6.10	70712	1.13	28.7	.164	4.2	29	5.1	.41	10	12	52	.56	14.1	0.038	1.0	14.6	MW	CG	N
0.240	6.10	70712S	1.13	28.7	.164	4.2	25	4.3	.32	8.2	7.9	35	.56	14.1	0.038	1.0	14.6	SST	CG	N
0.240	6.10	70732	1.13	28.7	.160	4.1	35	6.1	.39	9.9	14	60	.61	15.5	0.040	1.0	15.3	MW	CG	N
0.240	6.10	70732S	1.13	28.7	.160	4.1	30	5.2	.31	7.9	9.2	41	.61	15.5	0.040	1.0	15.3	SST	CG	N
0.240	6.10	70753	1.13	28.7	.156	4.0	42	7.4	.37	9.4	16	70	.66	16.7	0.042	1.1	15.6	MW	CG	N
0.240	6.10	70753S	1.13	28.7	.156	4.0	36	6.3	.29	7.5	11	47	.66	16.7	0.042	1.1	15.6	SST	CG	N
0.240	6.10	70772	1.13	28.7	.150	3.8	59	10	.32	8.2	19	85	.69	17.6	0.045	1.1	15.4	MW	CG	N
0.240	6.10	70772S	1.13	28.7	.150	3.8	50	8.8	.26	6.5	13	57	.69	17.6	0.045	1.1	15.4	SST	CG	N
0.240	6.10	70532	1.25	31.8	.208	5.3	1.1	.19	.94	24	1.0	4.6	.15	3.9	0.016	0.4	9.63	MW	CG	N
0.240	6.10	70532S	1.25	31.8	.208	5.3	.94	.16	.73	19	.68	3.0	.15	3.9	0.016	0.4	9.63	SST	CG	N
0.240	6.10	70549	1.25	31.8	.204	5.2	1.7	.30	.86	22	1.5	6.5	.18	4.6	0.018	0.5	10.1	MW	CG	N
0.240	6.10	70549S	1.25	31.8	.204	5.2	1.4	.25	.67	17	.97	4.3	.18	4.6	0.018	0.5	10.1	SST	CG	N
0.240	6.10	70571	1.25	31.8	.200	5.1	2.2	.38	.93	24	2.0	8.9	.24	6.1	0.020	0.5	12.0	MW	CG	N
0.240	6.10	70571S	1.25	31.8	.200	5.1	1.8	.32	.73	18	1.3	5.9	.24	6.1	0.020	0.5	12.0	SST	CG	N
0.240	6.10	70594	1.25	31.8	.196	5.0	3.3	.58	.80	20	2.6	12	.26	6.6	0.022	0.6	11.9	MW	CG	N
0.240	6.10	70594S	1.25	31.8	.196	5.0	2.8	.49	.63	16	1.8	7.8	.26	6.6	0.022	0.6	11.9	SST	CG	N
0.240	6.10	70614	1.25	31.8	.192	4.9	4.6	.80	.75	19	3.4	15	.30	7.5	0.024	0.6	12.4	MW	CG	N
0.240	6.10	70614S	1.25	31.8	.192	4.9	3.9	.68	.59	15	2.3	10	.30	7.5	0.024	0.6	12.4	SST	CG	N
0.240	6.10	70635	1.25	31.8	.188	4.8	5.9	1.0	.69	18	4.1	18	.35	8.8	0.026	0.7	13.4	MW	CG	N
0.240	6.10	70635S	1.25	31.8	.188	4.8	5.0	.88	.54	14	2.7	12	.35	8.8	0.026	0.7	13.4	SST	CG	N
0.240	6.10	70655	1.25	31.8	.182	4.6	8.8	1.5	.64	16	5.6	25	.42	10.6	0.029	0.7	14.4	MW	CG	N
0.240	6.10	70655S	1.25	31.8	.182	4.6	7.5	1.3	.50	13	3.8	17	.42	10.6	0.029	0.7	14.4	SST	CG	N
0.240	6.10	70674	1.25	31.8	.176	4.5	13	2.3	.58	15	7.5	33	.48	12.1	0.032	0.8	14.9	MW	CG	N
0.240	6.10	70674S	1.25	31.8	.176	4.5	11	1.9	.45	12	5.0	22	.48	12.1	0.032	0.8	14.9	SST	CG	N
0.240	6.10	70693	1.25	31.8	.170	4.3	18	3.1	.52	13	9.2	41	.56	14.2	0.035	0.9	16.0	MW	CG	N
0.240	6.10	70693S	1.25	31.8	.170	4.3	15	2.7	.41	10	6.3	28	.56	14.2	0.035	0.9	16.0	SST	CG	N
0.240	6.10	70713	1.25	31.8	.164	4.2	26	4.5	.45	11	12	52	.61	15.4	0.038	1.0	16.0	MW	CG	N
0.240	6.10	70713S	1.25	31.8	.164	4.2	22	3.9	.36	9.2	7.9	35	.61	15.4	0.038	1.0	16.0	SST	CG	N
0.240	6.10	70733	1.25	31.8	.160	4.1	31	5.4	.44	11	14	60	.68	17.1	0.040	1.0	16.9	MW	CG	N
0.240	6.10	70733S	1.25	31.8	.160	4.1	26	4.6	.35	8.9	9.2	41	.68	17.1	0.040	1.0	16.9	SST	CG	N



1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70656	1.38	35.1	.182	4.6	7.8	1.4	.72	18	5.6	25	.46	11.7	0.029	0.7	15.9	MW	CG	N
0.240	6.10	70656S	1.38	35.1	.182	4.6	6.6	1.2	.57	14	3.8	17	.46	11.7	0.029	0.7	15.9	SST	CG	N
0.240	6.10	70675	1.38	35.1	.176	4.5	12	2.0	.65	16	7.5	33	.53	13.4	0.032	0.8	16.5	MW	CG	N
0.240	6.10	70675S	1.38	35.1	.176	4.5	9.9	1.7	.51	13	5.0	22	.53	13.4	0.032	0.8	16.5	SST	CG	N
0.240	6.10	70694	1.38	35.1	.170	4.3	16	2.8	.58	15	9.2	41	.62	15.8	0.035	0.9	17.8	MW	CG	N
0.240	6.10	70694S	1.38	35.1	.170	4.3	14	2.4	.46	12	6.3	28	.62	15.8	0.035	0.9	17.8	SST	CG	N
0.240	6.10	70714	1.38	35.1	.164	4.2	23	4.1	.51	13	12	52	.67	17.0	0.038	1.0	17.6	MW	CG	N
0.240	6.10	70714S	1.38	35.1	.164	4.2	20	3.5	.40	10	7.9	35	.67	17.0	0.038	1.0	17.6	SST	CG	N
0.240	6.10	70734	1.38	35.1	.160	4.1	28	4.8	.49	13	14	60	.75	19.1	0.040	1.0	18.8	MW	CG	N
0.240	6.10	70734S	1.38	35.1	.160	4.1	23	4.1	.39	10	9.2	41	.75	19.1	0.040	1.0	18.8	SST	CG	N
0.240	6.10	70755	1.38	35.1	.156	4.0	34	6.0	.46	12	16	70	.80	20.3	0.042	1.1	19.0	MW	CG	N
0.240	6.10	70755S	1.38	35.1	.156	4.0	29	5.1	.37	9.3	11	47	.80	20.3	0.042	1.1	19.0	SST	CG	N
0.240	6.10	70533	1.50	38.1	.208	5.3	.90	.16	1.1	29	1.0	4.6	.18	4.6	0.016	0.4	11.4	MW	CG	N
0.240	6.10	70533S	1.50	38.1	.208	5.3	.77	.13	.89	23	.68	3.0	.18	4.6	0.016	0.4	11.4	SST	CG	N
0.240	6.10	70550	1.50	38.1	.204	5.2	1.4	.25	1.0	26	1.5	6.5	.21	5.4	0.018	0.5	11.9	MW	CG	N
0.240	6.10	70550S	1.50	38.1	.204	5.2	1.2	.21	.82	21	.97	4.3	.21	5.4	0.018	0.5	11.9	SST	CG	N
0.240	6.10	70574	1.50	38.1	.200	5.1	1.8	.31	1.1	28	2.0	8.9	.28	7.2	0.020	0.5	14.1	MW	CG	N
0.240	6.10	70574S	1.50	38.1	.200	5.1	1.5	.27	.87	22	1.3	5.9	.28	7.2	0.020	0.5	14.1	SST	CG	N
0.240	6.10	70597	1.50	38.1	.196	5.0	2.8	.49	.94	24	2.6	12	.30	7.6	0.022	0.6	13.6	MW	CG	N
0.240	6.10	70597S	1.50	38.1	.196	5.0	2.4	.42	.74	19	1.8	7.8	.30	7.6	0.022	0.6	13.6	SST	CG	N
0.240	6.10	70617	1.50	38.1	.192	4.9	3.7	.65	.92	23	3.4	15	.35	9.0	0.024	0.6	14.8	MW	CG	N
0.240	6.10	70617S	1.50	38.1	.192	4.9	3.2	.55	.72	18	2.3	10	.35	9.0	0.024	0.6	14.8	SST	CG	N
0.240	6.10	70638	1.50	38.1	.188	4.8	4.9	.86	.83	21	4.1	18	.41	10.3	0.026	0.7	15.6	MW	CG	N
0.240	6.10	70638S	1.50	38.1	.188	4.8	4.2	.73	.66	17	2.7	12	.41	10.3	0.026	0.7	15.6	SST	CG	N
0.240	6.10	70657	1.50	38.1	.182	4.6	7.3	1.3	.77	20	5.6	25	.49	12.4	0.029	0.7	16.9	MW	CG	N
0.240	6.10	70657S	1.50	38.1	.182	4.6	6.2	1.1	.61	15	3.8	17	.49	12.4	0.029	0.7	16.9	SST	CG	N
0.240	6.10	70676	1.50	38.1	.176	4.5	11	1.9	.70	18	7.5	33	.57	14.4	0.032	0.8	17.8	MW	CG	N
0.240	6.10	70676S	1.50	38.1	.176	4.5	9.1	1.6	.55	14	5.0	22	.57	14.4	0.032	0.8	17.8	SST	CG	N
0.240	6.10	70695	1.50	38.1	.170	4.3	15	2.6	.63	16	9.2	41	.67	16.9	0.035	0.9	19.0	MW	CG	N
0.240	6.10	70695S	1.50	38.1	.170	4.3	12	2.2	.50	13	6.3	28	.67	16.9	0.035	0.9	19.0	SST	CG	N
0.240	6.10	70715	1.50	38.1	.164	4.2	21	3.7	.55	14	12	52	.73	18.5	0.038	1.0	19.1	MW	CG	N
0.240	6.10	70715S	1.50	38.1	.164	4.2	18	3.2	.44	11	7.9	35	.73	18.5	0.038	1.0	19.1	SST	CG	N
0.240	6.10	70735	1.50	38.1	.160	4.1	25	4.5	.53	14	14	60	.81	20.4	0.040	1.0	20.1	MW	CG	N
0.240	6.10	70735S	1.50	38.1	.160	4.1	22	3.8	.43	11	9.2	41	.81	20.4	0.040	1.0	20.1	SST	CG	N
0.240	6.10	70756	1.50	38.1	.156	4.0	31	5.4	.51	13	16	70	.87	22.1	0.042	1.1	20.8	MW	CG	N
0.240	6.10	70756S	1.50	38.1	.156	4.0	26	4.6	.40	10	11	47	.87	22.1	0.042	1.1	20.8	SST	CG	N
0.240	6.10	70774	1.50	38.1	.150	3.8	43	7.6	.44	11	19	85	.91	23.1	0.045	1.1	20.3	MW	CG	N
0.240	6.10	70774S	1.50	38.1	.150	3.8	37	6.5	.35	8.9	13	57	.91	23.1	0.045	1.1	20.3	SST	CG	N
0.240	6.10	70534	1.75	44.5	.208	5.3	.80	.14	1.3	33	1.0	4.6	.20	5.1	0.016	0.4	12.5	MW	CG	N
0.240	6.10	70534S	1.75	44.5	.208	5.3	.68	.12	1.0	26	.68	3.0	.20	5.1	0.016	0.4	12.5	SST	CG	N
0.240	6.10	70551	1.75	44.5	.204	5.2	1.2	.21	1.2	31	1.5	6.5	.24	6.2	0.018	0.5	13.5	MW	CG	N
0.240	6.10	70551S	1.75	44.5	.204	5.2	1.0	.18	.95	24	.97	4.3	.24	6.2	0.018	0.5	13.5	SST	CG	N
0.240	6.10	70575	1.75	44.5	.200	5.1	1.5	.26	1.3	34	2.0	8.9	.33	8.3	0.020	0.5	16.3	MW	CG	N
0.240	6.10	70575S	1.75	44.5	.200	5.1	1.3	.22	1.0	26	1.3	5.9	.33	8.3	0.020	0.5	16.3	SST	CG	N
0.240	6.10	70598	1.75	44.5	.196	5.0	2.4	.41	1.1	29	2.6	12	.35	8.9	0.022	0.6	15.9	MW	CG	N
0.240	6.10	70598S	1.75	44.5	.196	5.0	2.0	.35	.88	22	1.8	7.8	.35	8.9	0.022	0.6	15.9	SST	CG	N
0.240	6.10	70618	1.75	44.5	.192	4.9	3.3	.57	1.1	27	3.4	15	.40	10.1	0.024	0.6	16.6	MW	CG	N
0.240	6.10	70618S	1.75	44.5	.192	4.9	2.8	.48	.82	21	2.3	10	.40	10.1	0.024	0.6	16.6	SST	CG	N
0.240	6.10	70639	1.75	44.5	.188	4.8	4.2	.73	.98	25	4.1	18	.47	12.0	0.026	0.7	18.1	MW	CG	N
0.240	6.10	70639S	1.75	44.5	.188	4.8	3.5	.62	.77	20	2.7	12	.47	12.0	0.026	0.7	18.1	SST	CG	N
0.240	6.10	70658	1.75	44.5	.182	4.6	6.2	1.1	.91	23	5.6	25	.57	14.4	0.029	0.7	19.5	MW	CG	N
0.240	6.10	70658S	1.75	44.5	.182	4.6	5.2	.92	.72	18	3.8	17	.57	14.4	0.029	0.7	19.5	SST	CG	N
0.240	6.10	70677	1.75	44.5	.176	4.5	9.2	1.6	.81	21	7.5	33	.65	16.5	0.032	0.8	20.3	MW	CG	N
0.240	6.10	70677S	1.75	44.5	.176	4.5	7.8	1.4	.64	16	5.0	22	.65	16.5	0.032	0.8	20.3	SST	CG	N
0.240	6.10	70696	1.75	44.5	.170	4.3	12	2.2	.75	19	9.2	41	.78	19.8	0.035	0.9	22.3	MW	CG	N
0.240	6.10	70696S	1.75	44.5	.170	4.3	11	1.8	.59	15	6.3	28	.78	19.8	0.035	0.9	22.3	SST	CG	N
0.240	6.10	70716	1.75	44.5	.164	4.2	18	3.1	.66	17	12	52	.86	21.8	0.038	1.0	22.6	MW	CG	N
0.240	6.10	70716S	1.75	44.5	.164	4.2	15	2.6	.53	13	7.9	35	.86	21.8	0.038	1.0	22.6	SST	CG	N
0.240	6.10	70736	1.75	44.5	.160	4.1	22	3.8	.63	16	14	60	.94	23.7	0.040	1.0	23.4	MW	CG	N
0.240	6.10	70736S	1.75	44.5	.160	4.1	18	3.2	.50	13	9.2	41	.94	23.7	0.040	1.0	23.4	SST	CG	N
0.240	6.10	70757	1.75	44.5	.156	4.0	27	4.6	.59	15	16	70	1.00	25.3	0.042	1.1	23.8	MW	CG	N
0.240	6.10	70757S	1.75	44.5	.156	4.0	23	3.9	.47	12	11	47	1.00	25.3	0.042	1.1	23.8	SST	CG	N
0.240	6.10	70775	1.75	44.5	.150	3.8	37	6.5	.52	13	19	85	1.06	26.9	0.045	1.1	23.5	MW	CG	N
0.240	6.10	70775S	1.75	44.5	.150	3.8	31	5.5	.41	10	13	57	1.06	26.9	0.045	1.1	23.5	SST	CG	N
0.240	6.10	70535	2.00	50.8	.208	5.3	.70	.12	1.5	37	1.0	4.6	.22	5.7	0.016	0.4	14.0	MW	CG	N
0.240	6.10	70535S	2.00	50.8	.208	5.3	.60	.10	1.2	29	.68	3.0	.22	5.7	0.016	0.4	14.0	SST	CG	N
0.240	6.10	70552	2.00	50.8	.204	5.2	1.0	.18	1.5	37	1.5	6.5	.28	7.2	0.018	0.5	15.8	MW	CG	N
0.240	6.10	70552S	2.00	50.8	.204	5.2	.85	.15</												



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.240	6.10	70697	2.00	50.8	.170	4.3	11	1.9	.85	22	9.2	41	.88	22.2	0.035	0.9	25.0	MW	CG	N
0.240	6.10	70697S	2.00	50.8	.170	4.3	9.3	1.6	.67	17	6.3	28	.88	22.2	0.035	0.9	25.0	SST	CG	N
0.240	6.10	70717	2.00	50.8	.164	4.2	16	2.7	.75	19	12	52	.96	24.5	0.038	1.0	25.4	MW	CG	N
0.240	6.10	70717S	2.00	50.8	.164	4.2	13	2.3	.60	15	7.9	35	.96	24.5	0.038	1.0	25.4	SST	CG	N
0.240	6.10	70737	2.00	50.8	.160	4.1	19	3.3	.72	18	14	60	1.05	26.7	0.040	1.0	26.3	MW	CG	N
0.240	6.10	70737S	2.00	50.8	.160	4.1	16	2.8	.57	15	9.2	41	1.05	26.7	0.040	1.0	26.3	SST	CG	N
0.240	6.10	70758	2.00	50.8	.156	4.0	23	4.0	.68	17	16	70	1.13	28.8	0.042	1.1	27.0	MW	CG	N
0.240	6.10	70758S	2.00	50.8	.156	4.0	20	3.4	.54	14	11	47	1.13	28.8	0.042	1.1	27.0	SST	CG	N
0.240	6.10	70776	2.00	50.8	.150	3.8	32	5.6	.59	15	19	85	1.20	30.6	0.045	1.1	26.8	MW	CG	N
0.240	6.10	70776S	2.00	50.8	.150	3.8	27	4.8	.47	12	13	57	1.20	30.6	0.045	1.1	26.8	SST	CG	N
0.240	6.10	70698	2.25	57.2	.170	4.3	9.7	1.7	.95	24	9.2	41	.98	24.8	0.035	0.9	27.9	MW	CG	N
0.240	6.10	70698S	2.25	57.2	.170	4.3	8.2	1.4	.76	19	6.3	28	.98	24.8	0.035	0.9	27.9	SST	CG	N
0.240	6.10	70718	2.25	57.2	.164	4.2	14	2.4	.85	22	12	52	1.08	27.5	0.038	1.0	28.5	MW	CG	N
0.240	6.10	70718S	2.25	57.2	.164	4.2	12	2.0	.68	17	7.9	35	1.08	27.5	0.038	1.0	28.5	SST	CG	N
0.240	6.10	70738	2.25	57.2	.160	4.1	17	2.9	.82	21	14	60	1.20	30.4	0.040	1.0	29.9	MW	CG	N
0.240	6.10	70738S	2.25	57.2	.160	4.1	14	2.5	.66	17	9.2	41	1.20	30.4	0.040	1.0	29.9	SST	CG	N
0.240	6.10	70759	2.25	57.2	.156	4.0	20	3.6	.76	19	16	70	1.27	32.1	0.042	1.1	30.1	MW	CG	N
0.240	6.10	70759S	2.25	57.2	.156	4.0	17	3.0	.61	15	11	47	1.27	32.1	0.042	1.1	30.1	SST	CG	N
0.240	6.10	70777	2.25	57.2	.150	3.8	28	5.0	.67	17	19	85	1.35	34.3	0.045	1.1	30.0	MW	CG	N
0.240	6.10	70777S	2.25	57.2	.150	3.8	24	4.2	.53	14	13	57	1.35	34.3	0.045	1.1	30.0	SST	CG	N
0.240	6.10	A12-23	2.34	59.5	.164	4.2	8.3	1.4	.56	14	4.6	21	1.79	45.4	0.038	1.0	46.0	MW	C	N
0.240	6.10	70699	2.50	63.5	.170	4.3	8.8	1.5	1.1	27	9.2	41	1.07	27.2	0.035	0.9	30.6	MW	CG	N
0.240	6.10	70699S	2.50	63.5	.170	4.3	7.4	1.3	.84	21	6.3	28	1.07	27.2	0.035	0.9	30.6	SST	CG	N
0.240	6.10	70719	2.50	63.5	.164	4.2	12	2.2	.95	24	12	52	1.20	30.5	0.038	1.0	31.6	MW	CG	N
0.240	6.10	70719S	2.50	63.5	.164	4.2	10	1.8	.76	19	7.9	35	1.20	30.5	0.038	1.0	31.6	SST	CG	N
0.240	6.10	70739	2.50	63.5	.160	4.1	15	2.6	.91	23	14	60	1.32	33.4	0.040	1.0	32.9	MW	CG	N
0.240	6.10	70739S	2.50	63.5	.160	4.1	13	2.2	.73	18	9.2	41	1.32	33.4	0.040	1.0	32.9	SST	CG	N
0.240	6.10	70760	2.50	63.5	.156	4.0	18	3.2	.87	22	16	70	1.42	36.1	0.042	1.1	33.9	MW	CG	N
0.240	6.10	70760S	2.50	63.5	.156	4.0	15	2.7	.69	18	11	47	1.42	36.1	0.042	1.1	33.9	SST	CG	N
0.240	6.10	70778	2.50	63.5	.150	3.8	25	4.4	.75	19	19	85	1.50	38.0	0.045	1.1	33.3	MW	CG	N
0.240	6.10	70778S	2.50	63.5	.150	3.8	22	3.8	.60	15	13	57	1.50	38.0	0.045	1.1	33.3	SST	CG	N
0.240	6.10	70740	3.25	82.6	.160	4.1	22	3.8	.63	16	14	60	.93	23.6	0.040	1.0	23.3	MW	CG	N
0.240	6.10	70740S	3.25	82.6	.160	4.1	18	3.2	.50	13	9.2	41	.93	23.6	0.040	1.0	23.3	SST	CG	N
0.240	6.10	70741	5.25	133.4	.160	4.1	17	2.9	.81	21	14	60	1.18	30.0	0.040	1.0	29.5	MW	CG	N
0.240	6.10	70741S	5.25	133.4	.160	4.1	14	2.5	.65	16	9.2	41	1.18	30.0	0.040	1.0	29.5	SST	CG	N
0.245	6.22	12691	3.67	93.2	.175	4.4	6.1	1.1	1.0	25	6.1	27	1.26	32.0	0.035	0.9	35.0	SST	C	N
0.250	6.35	B8-29	.16	4.0	.182	4.6	191	33	.03	.83	6.2	28	.10	2.6	0.034	0.9	3.00	SPR	CG	Z
0.250	6.35	10200	.19	4.8	.214	5.4	8.1	1.4	.11	2.7	.86	3.8	.08	2.1	0.018	0.5	3.50	MW	C	Z
0.250	6.35	A15-20	.19	4.8	.164	4.2	369	65	.03	.80	12	52	.15	3.8	0.043	1.1	3.50	SPR	CG	N
0.250	6.35	K-78	.22	5.6	.174	4.4	159	28	.05	1.2	7.7	34	.14	3.6	0.038	1.0	3.75	SST	CG	N
0.250	6.35	Q-94	.25	6.4	.222	5.6	.48	.08	.09	2.2	.04	.18	.16	4.2	0.014	0.4	10.8	MW	C	Z
0.250	6.35	10269	.25	6.4	.220	5.6	2.2	.39	.17	4.2	.37	1.7	.08	2.1	0.015	0.4	4.50	MW	C	N
0.250	6.35	U-24	.25	6.4	.200	5.1	16	2.9	.10	2.5	1.6	7.3	.15	3.8	0.025	0.6	5.00	MW	C	GI
0.250	6.35	CC-26	.25	6.4	.186	4.7	73	13	.09	2.3	6.5	29	.16	4.1	0.032	0.8	4.00	MW	C	N
0.250	6.35	L-40	.25	6.4	.178	4.5	123	22	.06	1.4	7.0	31	.14	3.7	0.036	0.9	4.00	SPR	CG	Z
0.250	6.35	DD-33	.28	7.1	.220	5.6	.98	.17	.18	4.5	.17	.76	.11	2.7	0.015	0.4	7.00	SST	CG	N
0.250	6.35	G-83	.28	7.1	.214	5.4	4.0	.71	.17	4.4	.70	3.1	.11	2.7	0.018	0.5	5.00	MW	C	GI
0.250	6.35	DD-63	.28	7.1	.210	5.3	6.3	1.1	.16	4.1	1.0	4.5	.12	3.0	0.020	0.5	5.00	MW	C	N
0.250	6.35	F-49	.28	7.1	.188	4.8	56	9.8	.08	2.0	4.4	20	.16	3.9	0.031	0.8	4.00	SST	C	N
0.250	6.35	S-116	.31	7.9	.226	5.7	.32	.06	.20	5.2	.07	.29	.11	2.7	0.012	0.3	8.00	SST	C	N
0.250	6.35	MM-9	.31	7.9	.210	5.3	5.5	.96	.21	5.4	1.2	5.2	.10	2.5	0.020	0.5	5.00	SST	C	N
0.250	6.35	A9-3	.31	7.9	.190	4.8	42	7.3	.10	2.4	4.0	18	.13	3.3	0.030	0.8	4.33	SST	CG	N
0.250	6.35	AA-16	.31	7.9	.190	4.8	27	4.8	.13	3.4	3.6	16	.18	4.6	0.030	0.8	6.00	MW	CG	Z
0.250	6.35	O-158	.31	7.9	.188	4.8	44	7.7	.10	2.5	4.4	20	.14	3.5	0.031	0.8	4.50	SST	CG	N
0.250	6.35	F-94	.31	7.9	.186	4.7	58	10	.09	2.3	5.2	23	.18	4.5	0.032	0.8	4.50	SPR	C	Z
0.250	6.35	B15-10	.31	7.9	.186	4.7	48	8.5	.11	2.7	5.2	23	.16	4.1	0.032	0.8	5.00	SPR	CG	Z
0.250	6.35	A15-8	.34	8.7	.172	4.4	105	18	.08	2.0	8.2	37	.20	5.0	0.039	1.0	5.00	SST	CG	N
0.250	6.35	RR-25	.34	8.7	.170	4.3	265	46	.04	.91	9.5	42	.18	4.6	0.040	1.0	3.50	SPR	C	N
0.250	6.35	PP-17	.34	8.7	.164	4.2	185	32	.06	1.6	12	52	.22	5.5	0.043	1.1	5.00	SPR	CG	GI
0.250	6.35	Z-2	.38	9.5	.210	5.3	3.7	.64	.23	5.7	.82	3.7	.15	3.8	0.020	0.5	6.50	SST	C	N
0.250	6.35	CC-63	.38	9.5	.210	5.3	6.7	1.2	.19	4.8	1.3	5.7	.09	2.3	0.020	0.5	4.50	SST	CG	N
0.250	6.35	LL-85	.38	9.5	.208	5.3	5.8	1.0	.23	5.8	1.3	5.9	.15	3.7	0.021	0.5	6.00	MW	C	N
0.250	6.35	EE-49	.38	9.5	.202	5.1	10	1.8	.21	5.3	2.1	9.5	.17	4.3	0.024	0.6	6.00	MW	C	Z
0.250	6.35	PP-55	.38	9.5	.202	5.1	14	2.4	.23	5.9	3.2	14	.14	3.7	0.024	0.6	5.00	MW	C	Z
0.250	6.35	II-41	.38	9.5	.198	5.0	19	3.4	.20	5.1	3.9	17	.16	4.0	0.026	0.7	5.00	MW	C	N
0.250	6.35	11366	.38	9.5	.194	4.9	19	3.3	.17	4.3	3.3	15	.16	4.1	0.028	0.7	5.75	SST	CG	N
0.250	6.35	BB-22	.38	9.5	.188	4.8	27	4.8	.16	4.1	4.4	20	.19	4.7	0.031	0.8	6.00	SST	CG	N
0.250	6.35	AA-39	.38	9.5	.186	4.7	42	7.4	.11	2.9	4.8	21	.16	4.1	0.032	0.8	5.00	SST	CG	N
0.250	6.35	3566	.38	9.5	.180	4.6	54	9.5	.16	4.2	8.9	40</								



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	CC-43	.44	11.1	.210	5.3	3.3	.58	.28	7.1	.91	4.1	.16	4.1	0.020	0.5	7.00	SST	C	N
0.250	6.35	L-14	.44	11.1	.210	5.3	2.3	.41	.24	6.0	.56	2.5	.20	5.1	0.020	0.5	9.00	SST	C	N
0.250	6.35	2821	.44	11.1	.206	5.2	8.1	1.4	.30	7.5	2.4	11	.14	3.6	0.022	0.6	5.50	MW	C	Z
0.250	6.35	AA-13	.44	11.1	.206	5.2	7.1	1.2	.28	7.2	2.0	9.0	.15	3.9	0.022	0.6	6.00	MW	C	Z
0.250	6.35	B18-156	.44	11.1	.202	5.1	12	2.1	.28	7.1	3.3	15	.13	3.4	0.024	0.6	5.50	MW	CG	N
0.250	6.35	F-97	.44	11.1	.200	5.1	14	2.5	.25	6.3	3.5	16	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.250	6.35	B5-24	.44	11.1	.194	4.9	20	3.5	.24	6.2	4.9	22	.13	3.4	0.028	0.7	6.00	MW	CG	N
0.250	6.35	F-25	.44	11.1	.184	4.7	48	8.3	.12	3.0	5.7	25	.21	5.4	0.033	0.8	5.50	SPR	C	Z
0.250	6.35	A12-22	.47	11.9	.228	5.8	.26	.05	.37	9.4	.09	.42	.10	2.5	0.011	0.3	8.00	MW	C	Z
0.250	6.35	V-98	.47	11.9	.212	5.4	1.9	.34	.30	7.5	.57	2.5	.17	4.3	0.019	0.5	9.00	SST	CG	N
0.250	6.35	4278	.47	11.9	.210	5.3	3.8	.66	.31	7.8	1.2	5.2	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.250	6.35	BB-74	.47	11.9	.210	5.3	2.8	.49	.31	7.8	.86	3.8	.16	4.1	0.020	0.5	8.00	SST	CG	N
0.250	6.35	G-98	.47	11.9	.206	5.2	7.2	1.3	.23	6.0	1.7	7.5	.12	3.1	0.022	0.6	5.50	SST	CG	N
0.250	6.35	L-92	.47	11.9	.190	4.8	22	3.8	.19	4.7	4.0	18	.20	5.0	0.030	0.8	6.50	SST	CG	N
0.250	6.35	F-23	.47	11.9	.184	4.7	42	7.3	.14	3.5	5.7	25	.23	5.9	0.033	0.8	6.00	SPR	C	Z
0.250	6.35	J-71	.47	11.9	.172	4.4	71	12	.12	3.2	8.8	39	.27	6.9	0.039	1.0	7.00	SPR	CG	Z
0.250	6.35	J-72	.47	11.9	.168	4.3	89	16	.11	2.9	10	45	.29	7.3	0.041	1.0	7.00	SPR	CG	N
0.250	6.35	B15-3	.47	11.9	.120	3.0	1351	237	.03	.65	34	153	.33	8.3	0.065	1.7	5.00	SPR	CG	N
0.250	6.35	S-794	.50	12.7	.210	5.3	3.5	.61	.35	8.8	1.2	5.3	.16	3.9	0.020	0.5	6.75	SST	C	N
0.250	6.35	V-100	.50	12.7	.210	5.3	3.2	.55	.32	8.1	1.0	4.5	.18	4.6	0.020	0.5	8.00	MW	C	N
0.250	6.35	H-94	.50	12.7	.208	5.3	3.1	.54	.30	7.5	.90	4.0	.20	5.2	0.021	0.5	8.75	SST	C	N
0.250	6.35	S-717	.50	12.7	.206	5.2	6.6	1.2	.26	6.5	1.7	7.5	.15	3.8	0.022	0.6	5.75	SST	C	N
0.250	6.35	BB-16	.50	12.7	.204	5.2	7.5	1.3	.26	6.5	1.9	8.6	.16	4.1	0.023	0.6	6.00	SST	C	N
0.250	6.35	HH-84	.50	12.7	.204	5.2	4.6	.81	.28	7.2	1.3	5.8	.22	5.5	0.023	0.6	8.50	SST	C	N
0.250	6.35	B15-68	.50	12.7	.204	5.2	4.4	.76	.29	7.4	1.3	5.7	.21	5.3	0.023	0.6	9.00	SST	CG	N
0.250	6.35	GG-46	.50	12.7	.202	5.1	10	1.8	.32	8.1	3.3	15	.17	4.3	0.024	0.6	6.00	MW	C	Z
0.250	6.35	3985	.50	12.7	.200	5.1	16	2.9	.21	5.4	3.5	16	.15	3.8	0.025	0.6	5.00	MW	C	Z
0.250	6.35	F-13	.50	12.7	.200	5.1	12	2.2	.28	7.2	3.5	16	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.250	6.35	S-1178	.50	12.7	.200	5.1	14	2.5	.16	4.2	2.3	10	.15	3.8	0.025	0.6	5.00	SST	C	N
0.250	6.35	Z-53	.50	12.7	.200	5.1	11	1.9	.22	5.5	2.3	10	.18	4.4	0.025	0.6	6.00	SST	C	N
0.250	6.35	B2-9	.50	12.7	.200	5.1	9.9	1.7	.30	7.6	3.0	13	.20	5.1	0.025	0.6	7.00	MW	C	N
0.250	6.35	2532	.50	12.7	.198	5.0	12	2.0	.29	7.4	3.4	15	.21	5.3	0.026	0.7	7.00	MW	C	Z
0.250	6.35	HH-13	.50	12.7	.196	5.0	8.6	1.5	.26	6.5	2.2	9.8	.24	6.2	0.027	0.7	9.00	SST	CG	N
0.250	6.35	XX-63	.50	12.7	.196	5.0	11	2.0	.26	6.5	3.0	13	.24	6.2	0.027	0.7	8.00	MW	C	Z
0.250	6.35	12734	.50	12.7	.192	4.9	17	3.0	.21	5.3	3.6	16	.20	5.0	0.029	0.7	6.75	SST	CG	N
0.250	6.35	B9-16	.50	12.7	.192	4.9	19	3.3	.29	7.3	5.4	24	.20	5.2	0.029	0.7	7.00	MW	CG	Z
0.250	6.35	NN-59	.50	12.7	.190	4.8	22	3.8	.26	6.6	5.7	25	.24	6.1	0.030	0.8	7.00	MW	CL	N
0.250	6.35	2556	.50	12.7	.186	4.7	29	5.1	.18	4.5	5.2	23	.26	6.5	0.032	0.8	7.00	HD	C	Z
0.250	6.35	529	.50	12.7	.180	4.6	42	7.4	.15	3.7	6.2	28	.29	7.2	0.035	0.89	7.13	HD	C	Z
0.250	6.35	NN-15	.50	12.7	.180	4.6	54	9.5	.12	3.0	6.4	29	.25	6.2	0.035	0.9	6.00	SPR	C	Z
0.250	6.35	NN-73	.50	12.7	.180	4.6	28	4.8	.19	4.7	5.1	23	.32	8.0	0.035	0.9	9.00	SST	CG	N
0.250	6.35	FF-13	.50	12.7	.180	4.6	31	5.5	.19	4.9	6.0	27	.28	7.1	0.035	0.9	8.00	SST	CG	N
0.250	6.35	A9-11	.50	12.7	.178	4.5	49	8.6	.14	3.6	7.0	31	.25	6.4	0.036	0.9	7.00	SPR	CG	N
0.250	6.35	B1-48	.50	12.7	.172	4.4	64	11	.14	3.5	8.8	39	.29	7.4	0.039	1.0	7.50	SPR	CG	N
0.250	6.35	O-155	.50	12.7	.172	4.4	79	14	.11	2.8	8.8	39	.29	7.4	0.039	1.0	6.50	SPR	C	Z
0.250	6.35	BB-9	.50	12.7	.170	4.3	58	10	.15	3.9	8.9	39	.32	8.1	0.040	1.0	8.00	SST	CG	N
0.250	6.35	518	.50	12.7	.168	4.3	85	15	.12	3.0	10	45	.34	8.6	0.041	1.0	7.25	HD	C	Z
0.250	6.35	FF-81	.50	12.7	.160	4.1	144	25	.09	2.3	13	59	.30	7.7	0.045	1.1	6.75	SPR	CG	Z
0.250	6.35	I-83	.50	12.7	.158	4.0	126	22	.11	2.8	14	63	.37	9.3	0.046	1.2	8.00	SPR	CG	N
0.250	6.35	NN-48	.50	12.7	.142	3.6	353	62	.06	1.4	20	87	.32	8.2	0.054	1.4	6.00	SST	CG	N
0.250	6.35	L-100	.50	12.7	.130	3.3	429	75	.05	1.3	21	96	.45	11.4	0.060	1.5	7.50	SST	CG	N
0.250	6.35	00-58	.52	13.1	.210	5.3	4.7	.83	.38	9.5	1.8	7.9	.14	3.6	0.020	0.5	6.00	MW	C	N
0.250	6.35	S-163	.53	13.5	.214	5.4	1.8	.31	.37	9.4	.66	2.9	.16	4.1	0.018	0.5	8.00	SST	C	N
0.250	6.35	Q-14	.53	13.5	.192	4.9	13	2.4	.27	6.9	3.6	16	.26	6.6	0.029	0.7	9.00	MW	CG	Z
0.250	6.35	2929	.53	13.5	.180	4.6	54	9.5	.12	3.0	6.4	29	.25	6.2	0.035	0.9	6.00	SPR	C	Z
0.250	6.35	S-31	.53	13.5	.180	4.6	32	5.6	.19	4.8	6.0	27	.32	8.0	0.035	0.9	8.00	SST	C	N
0.250	6.35	2611	.53	13.5	.176	4.5	70	12	.15	3.8	10	47	.22	5.6	0.037	0.9	6.00	MW	CG	Z
0.250	6.35	A-23	.53	13.5	.172	4.4	54	9.4	.15	3.9	8.2	37	.30	7.7	0.039	1.0	7.75	SST	CG	N
0.250	6.35	A14-9	.53	13.5	.172	4.4	59	10	.15	3.8	8.8	39	.31	7.9	0.039	1.0	8.00	SPR	CG	GI
0.250	6.35	NN-39	.53	13.5	.170	4.3	79	14	.12	3.0	9.5	42	.32	8.1	0.040	1.0	7.00	SPR	C	N
0.250	6.35	EE-41	.53	13.5	.170	4.3	50	8.8	.17	4.3	8.6	38	.36	9.1	0.040	1.0	9.00	SST	CG	N
0.250	6.35	H-92	.53	13.5	.166	4.2	75	13	.14	3.4	10	45	.33	8.3	0.042	1.1	7.75	SST	CG	N
0.250	6.35	S-836	.53	13.5	.166	4.2	77	13	.13	3.4	10	45	.37	9.3	0.042	1.1	7.75	SST	C	N
0.250	6.35	O-62	.53	13.5	.150	3.8	160	28	.08	2.1	13	58	.45	11.4	0.050	1.3	9.00	SPR	CG	Z
0.250	6.35	AA-11	.55	13.9	.170	4.3	79	14	.12	3.0	9.5	42	.28	7.1	0.040	1.0	7.00	SPR	CG	Z
0.250	6.35	S-1239	.56	14.3	.218	5.5	.91	.16	.40	10	.37	1.6	.16	4.1	0.016	0.4	9.00	SST	C	N
0.250	6.35	J-10	.56	14.3	.206	5.2	4.1	.72	.36	9.2	1.5	6.7	.20	5.0	0.022	0.6	8.00	SST	C	N
0.250	6.35	F-50	.56	14.3	.194	4.9	12	2.0	.28	7.2	3.3	14	.28	7.1	0.028	0.7	9.00	MW	C	Z
0.250	6.35	926	.56	14.3	.186	4.7	26	4.6	.27	6.9	7.2	32	.27	6.9	0.032	0.8	7.50	MW	C	Z
0.250	6.35</																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	A-62	.63	15.9	.214	5.4	1.1	.18	.41	10	.43	1.9	.22	5.5	0.018	0.5	12.0	SST	CG	N
0.250	6.35	MM-96	.63	15.9	.214	5.4	3.5	.60	.41	10	1.4	6.2	.12	3.0	0.018	0.5	5.50	MW	C	Z
0.250	6.35	BB-61	.63	15.9	.210	5.3	3.2	.55	.47	12	1.5	6.5	.16	4.1	0.020	0.5	8.00	MW	CG	N
0.250	6.35	GG-47	.63	15.9	.210	5.3	4.2	.73	.30	7.7	1.3	5.7	.12	3.0	0.020	0.5	6.00	SST	CG	N
0.250	6.35	A15-2	.63	15.9	.206	5.2	5.7	1.0	.45	11	2.5	11	.15	3.9	0.022	0.6	7.00	MW	CG	N
0.250	6.35	AA-30	.63	15.9	.206	5.2	3.3	.58	.39	10	1.3	5.8	.23	5.9	0.022	0.6	9.50	SST	C	N
0.250	6.35	S-718	.63	15.9	.206	5.2	5.2	.91	.32	8.3	1.7	7.5	.17	4.3	0.022	0.6	6.75	SST	C	N
0.250	6.35	O-60	.63	15.9	.200	5.1	5.4	.94	.35	8.9	1.9	8.3	.28	7.0	0.025	0.6	10.0	SST	C	N
0.250	6.35	10383	.63	15.9	.194	4.9	12	2.0	.37	9.5	4.3	19	.25	6.4	0.028	0.7	9.00	MW	CG	N
0.250	6.35	W-5	.63	15.9	.194	4.9	12	2.0	.28	7.1	3.3	15	.22	5.7	0.028	0.7	8.00	SST	CG	N
0.250	6.35	1931	.63	15.9	.192	4.9	21	3.7	.26	6.6	5.4	24	.22	5.5	0.029	0.7	6.50	MW	C	Z
0.250	6.35	JJ-95	.63	15.9	.190	4.8	18	3.2	.33	8.3	6.0	27	.27	6.9	0.030	0.8	8.00	MW	C	N
0.250	6.35	PP-11	.63	15.9	.186	4.7	19	3.4	.25	6.3	4.8	21	.27	6.9	0.032	0.8	8.50	SST	CG	N
0.250	6.35	F-10	.63	15.9	.186	4.7	24	4.2	.21	5.4	5.2	23	.29	7.3	0.032	0.8	8.00	HD	C	Z
0.250	6.35	212	.63	15.9	.182	4.6	27	4.8	.23	5.8	6.2	28	.34	8.6	0.034	0.9	9.00	HD	C	Z
0.250	6.35	A14-28	.63	15.9	.182	4.6	30	5.3	.20	5.2	6.2	28	.28	7.1	0.034	0.9	8.25	SPR	CG	GI
0.250	6.35	Y-10	.63	15.9	.176	4.5	56	9.8	.14	3.4	7.6	34	.26	6.6	0.037	0.9	7.00	SPR	CG	Z
0.250	6.35	A13-9	.63	15.9	.164	4.2	81	14	.14	3.7	12	52	.38	9.7	0.043	1.1	8.88	SPR	CG	N
0.250	6.35	10475	.63	15.9	.160	4.1	114	20	.12	3.0	13	59	.41	10.3	0.045	1.1	8.00	SPR	C	Z
0.250	6.35	N-8	.66	16.7	.202	5.1	7.5	1.3	.44	11	3.3	15	.18	4.6	0.024	0.6	7.50	MW	CG	Z
0.250	6.35	B7-7	.66	16.7	.198	5.0	9.4	1.6	.42	11	3.9	17	.21	5.4	0.026	0.7	8.25	MW	CG	N
0.250	6.35	10554	.66	16.7	.196	5.0	7.9	1.4	.34	8.6	2.7	12	.32	8.1	0.027	0.7	10.8	MW	C	Z
0.250	6.35	935	.66	16.7	.188	4.8	21	3.7	.31	7.9	6.6	29	.28	7.1	0.031	0.8	8.00	MW	C	Z
0.250	6.35	2524	.66	16.7	.186	4.7	22	3.9	.23	5.9	5.2	23	.30	7.7	0.032	0.8	8.50	HD	C	Z
0.250	6.35	Z-56	.66	16.7	.186	4.7	14	2.5	.30	7.7	4.4	19	.35	8.9	0.032	0.8	11.0	SST	CG	N
0.250	6.35	A10-54	.66	16.7	.184	4.7	23	4.0	.23	5.9	5.3	23	.31	8.0	0.033	0.8	8.50	SPR	C	N
0.250	6.35	EE-81	.66	16.7	.176	4.5	40	7.0	.19	4.8	7.6	34	.33	8.5	0.037	0.9	9.00	SPR	CG	N
0.250	6.35	W-49	.66	16.7	.176	4.5	54	9.4	.13	3.3	7.1	32	.24	6.1	0.037	0.9	6.50	SST	CG	N
0.250	6.35	S-317	.69	17.4	.220	5.6	.54	.09	.51	13	.27	1.2	.18	4.6	0.015	0.4	11.0	SST	C	N
0.250	6.35	RR-46	.69	17.4	.210	5.3	3.3	.58	.39	9.9	1.3	5.7	.16	4.1	0.020	0.5	7.00	SST	C	N
0.250	6.35	KK-98	.69	17.4	.206	5.2	3.1	.54	.45	11	1.4	6.1	.24	6.1	0.022	0.6	10.0	SST	C	N
0.250	6.35	10609	.69	17.4	.202	5.1	6.4	1.1	.34	8.7	2.2	9.7	.21	5.3	0.024	0.6	7.75	SST	C	N
0.250	6.35	F-1	.69	17.4	.200	5.1	8.2	1.4	.43	11	3.5	16	.23	5.7	0.025	0.6	8.00	MW	C	Z
0.250	6.35	B1-44	.69	17.4	.198	5.0	8.3	1.5	.32	8.0	2.6	12	.21	5.4	0.026	0.7	8.25	SST	CG	N
0.250	6.35	HH-32	.69	17.4	.190	4.8	13	2.3	.34	8.7	4.4	20	.35	8.8	0.030	0.8	10.5	MW	C	Z
0.250	6.35	KK-24	.69	17.4	.190	4.8	11	1.9	.30	7.5	3.2	14	.39	9.9	0.030	0.8	12.0	MW	C	N
0.250	6.35	J-98	.69	17.4	.188	4.8	17	3.0	.26	6.5	4.4	20	.29	7.5	0.031	0.8	8.50	SST	C	N
0.250	6.35	J-49	.69	17.4	.186	4.7	21	3.6	.35	8.8	7.2	32	.32	8.1	0.032	0.8	9.00	MW	C	Z
0.250	6.35	B18-139	.69	17.4	.178	4.5	49	8.6	.14	3.6	7.0	31	.25	6.4	0.036	0.9	7.00	SPR	CG	Z
0.250	6.35	HH-94	.69	17.4	.174	4.4	36	6.4	.21	5.3	7.7	34	.36	9.2	0.038	1.0	9.50	SST	CG	N
0.250	6.35	AA-27	.69	17.4	.170	4.3	50	8.8	.18	4.5	8.9	39	.36	9.1	0.040	1.0	9.00	SST	CG	N
0.250	6.35	3584	.69	17.4	.166	4.2	66	12	.23	5.8	15	67	.40	10.1	0.042	1.1	9.50	MW	CG	GI
0.250	6.35	B1-4	.69	17.4	.164	4.2	74	13	.16	4.0	12	52	.41	10.4	0.043	1.1	9.50	SPR	CG	GI
0.250	6.35	V-22	.72	18.2	.212	5.4	3.0	.53	.54	14	1.6	7.3	.15	3.9	0.019	0.5	7.00	MW	C	Z
0.250	6.35	B15-53	.72	18.2	.172	4.4	51	8.9	.17	4.4	8.8	39	.39	9.9	0.039	1.0	9.00	SPR	C	N
0.250	6.35	B3-46	.73	18.6	.168	4.3	39	6.8	.20	5.1	7.8	35	.53	13.5	0.041	1.0	12.0	SST	C	N
0.250	6.35	W-53	.75	19.1	.210	5.3	1.6	.29	.49	12	.81	3.6	.26	6.6	0.020	0.5	12.0	SST	C	N
0.250	6.35	J-54	.75	19.1	.206	5.2	1.9	.34	.38	9.7	.74	3.3	.37	9.3	0.022	0.6	16.7	MW	CG	N
0.250	6.35	S-719	.75	19.1	.206	5.2	4.1	.72	.41	10	1.7	7.5	.20	5.0	0.022	0.6	8.00	SST	C	N
0.250	6.35	Q-89	.75	19.1	.206	5.2	4.5	.80	.56	14	2.5	11	.18	4.6	0.022	0.6	8.25	MW	CG	N
0.250	6.35	A15-45	.75	19.1	.204	5.2	4.9	.85	.39	10	1.9	8.6	.19	4.8	0.023	0.6	8.25	SST	CG	N
0.250	6.35	B2-12	.75	19.1	.204	5.2	3.7	.65	.50	13	1.9	8.3	.25	6.4	0.023	0.6	10.0	SST	CL	N
0.250	6.35	A14-20	.75	19.1	.202	5.1	6.9	1.2	.48	12	3.3	15	.19	4.9	0.024	0.6	8.00	MW	CG	GI
0.250	6.35	F-41	.75	19.1	.198	5.0	8.3	1.5	.47	12	3.9	17	.26	6.6	0.026	0.7	9.00	MW	CG	Z
0.250	6.35	2977	.75	19.1	.194	4.9	10	1.8	.44	11	4.5	20	.31	7.8	0.028	0.7	10.0	MW	C	Z
0.250	6.35	N-60	.75	19.1	.188	4.8	18	3.2	.36	9.2	6.6	29	.28	7.1	0.031	0.8	9.00	MW	CG	Z
0.250	6.35	Q-67	.75	19.1	.188	4.8	18	3.2	.36	9.2	6.6	29	.31	7.9	0.031	0.8	9.00	MW	C	N
0.250	6.35	3733	.75	19.1	.186	4.7	18	3.2	.29	7.2	5.2	23	.35	8.9	0.032	0.8	10.0	HD	C	Z
0.250	6.35	K-58	.75	19.1	.186	4.7	17	3.0	.30	7.7	5.2	23	.37	9.3	0.032	0.8	10.5	HD	C	GI
0.250	6.35	S-720	.75	19.1	.186	4.7	16	2.9	.30	7.5	4.8	21	.34	8.7	0.032	0.8	9.75	SST	C	N
0.250	6.35	H-19	.75	19.1	.186	4.7	15	2.5	.36	9.1	5.2	23	.38	9.8	0.032	0.8	12.0	HD	CG	N
0.250	6.35	W-83	.75	19.1	.184	4.7	18	3.2	.29	7.4	5.3	23	.36	9.2	0.033	0.8	10.0	SST	C	N
0.250	6.35	F-9	.75	19.1	.184	4.7	22	3.9	.26	6.5	5.7	25	.35	8.8	0.033	0.8	9.50	SPR	C	Z
0.250	6.35	K-90	.75	19.1	.180	4.6	29	5.1	.22	5.6	6.4	29	.33	8.4	0.035	0.9	9.50	SPR	CG	Z
0.250	6.35	B2-15	.75	19.1	.180	4.6	39	6.9	.23	5.7	8.9	40	.30	7.6	0.035	0.9	7.50	MW	C	N
0.250	6.35	B14-10	.75	19.1	.176	4.5	27	4.8	.26	6.5	7.1	32	.41	10.3	0.037	0.9	11.0	SST	CG	N
0.250	6.35	G-13	.75	19.1	.174	4.4	33	5.7	.23	5.9	7.7	34	.40	10.1	0.038	1.0	10.5	SST	CG	N
0.250	6.35	K-28	.75	19.1	.168	4.3	74	13	.14	3.5	10	45	.37	9.4	0.041	1.0	8.00	SPR	C	N
0.250	6.35	A15-10	.75	19.1	.166	4.2	52	9.1	.20	5.0	10	45	.44	11.2	0.042	1.1	10.5	SST	CG	N
0.250	6.35	NN-75	.75	19.1	.160	4.1	66	12	.19	4.8										




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	S-60	.81	20.6	.230	5.8	.10	.02	.69	18	.07	.31	.12	3.0	0.010	0.3	11.0	SST	C	N
0.250	6.35	B-69	.81	20.6	.218	5.5	.72	.13	.60	15	.43	1.9	.21	5.4	0.016	0.4	12.3	MW	C	N
0.250	6.35	A11-18	.81	20.6	.204	5.2	5.3	.93	.55	14	2.9	13	.20	5.0	0.023	0.6	8.50	MW	CG	GI
0.250	6.35	J-92	.81	20.6	.202	5.1	5.2	.90	.55	14	2.8	13	.26	6.7	0.024	0.6	10.0	MW	C	Z
0.250	6.35	B14-65	.81	20.6	.202	5.1	5.5	.96	.58	15	3.2	14	.23	5.8	0.024	0.6	9.50	MW	CG	N
0.250	6.35	YY-14	.81	20.6	.196	5.0	8.6	1.5	.51	13	4.4	19	.30	7.5	0.027	0.7	10.0	MW	CG	N
0.250	6.35	4289	.81	20.6	.194	4.9	8.1	1.4	.48	12	3.8	17	.34	8.5	0.028	0.7	12.0	MW	CG	Z
0.250	6.35	HH-5	.81	20.6	.186	4.7	14	2.5	.33	8.5	4.8	21	.34	8.7	0.032	0.8	10.8	SST	CG	N
0.250	6.35	F-8	.81	20.6	.184	4.7	20	3.4	.29	7.3	5.7	25	.38	9.6	0.033	0.8	10.5	SPR	C	Z
0.250	6.35	B-58	.81	20.6	.182	4.6	25	4.5	.24	6.2	6.2	28	.36	9.1	0.034	0.9	9.50	SPR	C	N
0.250	6.35	BB-23	.81	20.6	.180	4.6	19	3.3	.32	8.1	6.0	27	.46	11.6	0.035	0.9	12.0	SST	C	N
0.250	6.35	3866	.81	20.6	.172	4.4	35	6.2	.25	6.3	8.8	39	.47	11.9	0.039	1.0	12.0	SPR	CG	Z
0.250	6.35	A11-24	.81	20.6	.172	4.4	39	6.9	.22	5.7	8.8	39	.43	10.9	0.039	1.0	11.0	SPR	CG	N
0.250	6.35	A15-21	.81	20.6	.172	4.4	35	6.1	.24	6.0	8.2	37	.43	10.9	0.039	1.0	11.0	SST	CG	N
0.250	6.35	AA-99	.81	20.6	.156	4.0	93	16	.16	4.1	15	67	.52	13.1	0.047	1.2	11.0	SPR	CG	GI
0.250	6.35	S-486	.81	20.6	.124	3.1	376	66	.08	2.0	30	132	.63	16.0	0.063	1.6	10.0	SST	CG	N
0.250	6.35	S-9	.81	20.6	.100	2.5	941	165	.05	1.2	44	196	.75	19.1	0.075	1.9	10.0	SST	CG	N
0.250	6.35	J-23	.84	21.4	.198	5.0	7.3	1.3	.54	14	3.9	17	.26	6.6	0.026	0.7	10.0	MW	CG	Z
0.250	6.35	F-40	.84	21.4	.186	4.7	17	2.9	.31	7.9	5.2	23	.38	9.6	0.032	0.8	10.8	HD	C	Z
0.250	6.35	H-10	.84	21.4	.182	4.6	27	4.8	.23	5.8	6.2	28	.31	7.8	0.034	0.9	9.00	SPR	CG	GI
0.250	6.35	S-1313	.88	22.2	.224	5.7	.38	.07	.75	19	.29	1.3	.13	3.3	0.013	0.3	9.00	SST	C	N
0.250	6.35	AA-21	.88	22.2	.220	5.6	.81	.14	.67	17	.54	2.4	.14	3.4	0.015	0.4	8.00	SST	C	N
0.250	6.35	W-62	.88	22.2	.200	5.1	4.8	.83	.49	12	2.3	10	.28	7.0	0.025	0.6	11.0	SST	CG	N
0.250	6.35	2948	.88	22.2	.198	5.0	6.7	1.2	.59	15	3.9	17	.28	7.1	0.026	0.7	10.8	MW	CG	Z
0.250	6.35	F-91	.88	22.2	.198	5.0	7.3	1.3	.54	14	3.9	17	.29	7.3	0.026	0.7	10.0	MW	C	Z
0.250	6.35	A13-3	.88	22.2	.196	5.0	7.4	1.3	.40	10	2.9	13	.28	7.0	0.027	0.7	10.3	SST	CG	N
0.250	6.35	FF-98	.88	22.2	.194	4.9	12	2.0	.42	11	4.9	22	.28	7.1	0.028	0.7	9.00	MW	CG	Z
0.250	6.35	00-4	.88	22.2	.190	4.8	12	2.0	.52	13	6.0	27	.35	8.8	0.030	0.8	11.5	MW	CG	GI
0.250	6.35	S-721	.88	22.2	.186	4.7	14	2.4	.35	9.0	4.8	21	.39	10.0	0.032	0.8	11.3	SST	C	N
0.250	6.35	927	.88	22.2	.182	4.6	21	3.7	.29	7.4	6.2	28	.37	9.5	0.034	0.9	11.0	HD	CG	Z
0.250	6.35	10285	.88	22.2	.180	4.6	25	4.3	.26	6.6	6.4	29	.41	10.4	0.035	0.9	10.8	SPR	C	Z
0.250	6.35	B7-27	.88	22.2	.180	4.6	23	4.0	.28	7.2	6.4	29	.40	10.2	0.035	0.9	11.5	SPR	CG	N
0.250	6.35	928	.88	22.2	.168	4.3	49	8.7	.21	5.2	10	45	.49	12.5	0.041	1.0	11.0	HD	C	Z
0.250	6.35	S-723	.88	22.2	.166	4.2	43	7.6	.24	6.0	10	45	.55	13.9	0.042	1.1	12.0	SST	C	N
0.250	6.35	3874	.88	22.2	.114	2.9	850	149	.05	1.2	39	172	.54	13.8	0.068	1.7	8.00	SPR	CG	Z
0.250	6.35	B14-11	.91	23.0	.184	4.7	49	8.6	.11	2.7	5.3	23	.20	5.0	0.033	0.8	5.00	SST	C	N
0.250	6.35	10412	.91	23.0	.174	4.4	33	5.8	.25	6.3	8.2	36	.44	11.1	0.038	1.0	11.5	SPR	CG	Z
0.250	6.35	11899	.91	23.0	.160	4.1	76	13	.17	4.4	13	59	.54	13.7	0.045	1.1	11.0	SPR	C	N
0.250	6.35	10149	.94	23.8	.210	5.3	1.7	.29	.65	17	1.1	4.9	.29	7.2	0.020	0.5	13.3	MW	C	Z
0.250	6.35	O-314	.94	23.8	.202	5.1	4.4	.78	.64	16	2.8	13	.30	7.5	0.024	0.6	11.3	MW	C	Z
0.250	6.35	KK-43	.94	23.8	.198	5.0	6.5	1.1	.60	15	3.9	17	.31	7.9	0.026	0.7	11.0	MW	C	N
0.250	6.35	B5-65	.94	23.8	.196	5.0	6.3	1.1	.56	14	3.5	16	.38	9.6	0.027	0.7	13.0	MW	C	N
0.250	6.35	FF-89	.94	23.8	.190	4.8	9.9	1.7	.52	13	5.1	23	.42	10.7	0.030	0.8	13.0	MW	C	Z
0.250	6.35	L-84	.94	23.8	.190	4.8	11	1.9	.55	14	6.0	27	.39	9.9	0.030	0.8	12.0	MW	C	Z
0.250	6.35	F-39	.94	23.8	.186	4.7	15	2.5	.36	9.1	5.2	23	.42	10.6	0.032	0.8	12.0	SPR	C	Z
0.250	6.35	FF-50	.94	23.8	.180	4.6	20	3.6	.30	7.5	6.0	27	.39	10.0	0.035	0.9	11.3	SST	CG	N
0.250	6.35	2833	.94	23.8	.160	4.1	71	12	.26	6.6	18	82	.52	13.3	0.045	1.1	11.6	MW	CG	Z
0.250	6.35	S-930	.94	23.8	.158	4.0	73	13	.18	4.6	13	59	.55	14.0	0.046	1.2	11.0	SST	C	N
0.250	6.35	B-47	.94	23.8	.150	3.8	103	18	.15	3.9	16	70	.58	14.6	0.050	1.3	11.5	SST	CG	N
0.250	6.35	3519	.94	23.8	.138	3.5	176	31	.18	4.6	32	142	.73	18.5	0.056	1.4	13.0	MW	CG	Z
0.250	6.35	DD-43	.97	24.6	.210	5.3	1.7	.29	.71	18	1.2	5.3	.26	6.6	0.020	0.5	12.0	SST	C	N
0.250	6.35	3115	1.00	25.4	.214	5.4	1.3	.22	.78	20	.99	4.4	.23	5.7	0.018	0.5	11.5	MW	C	GI
0.250	6.35	W-47	1.00	25.4	.214	5.4	1.2	.20	.78	20	.92	4.1	.22	5.5	0.018	0.5	11.0	SST	C	N
0.250	6.35	151-A	1.00	25.4	.210	5.3	2.8	.49	.68	17	1.9	8.5	.20	5.0	0.020	0.5	8.75	MW	C	Z
0.250	6.35	3811	1.00	25.4	.210	5.3	2.4	.41	.78	20	1.8	8.2	.22	5.6	0.020	0.5	10.0	MW	C	GI
0.250	6.35	HH-67	1.00	25.4	.210	5.3	3.4	.59	.38	9.7	1.3	5.7	.16	4.1	0.020	0.5	7.00	SST	C	N
0.250	6.35	W-9	1.00	25.4	.210	5.3	1.5	.26	.72	18	1.1	4.8	.28	7.1	0.020	0.5	13.0	SST	C	N
0.250	6.35	4111	1.00	25.4	.208	5.3	1.9	.33	.67	17	1.3	5.6	.33	8.3	0.021	0.5	14.5	MW	C	Z
0.250	6.35	12667	1.00	25.4	.206	5.2	3.8	.66	.67	17	2.5	11	.21	5.3	0.022	0.6	9.50	MW	CG	N
0.250	6.35	3614	1.00	25.4	.204	5.2	3.1	.55	.68	17	2.1	9.4	.32	8.2	0.023	0.6	13.0	MW	C	Z
0.250	6.35	Q-68	1.00	25.4	.204	5.2	4.0	.71	.72	18	2.9	13	.24	6.1	0.023	0.6	10.5	MW	CG	N
0.250	6.35	12786	1.00	25.4	.196	5.0	6.3	1.1	.62	16	3.9	17	.38	9.6	0.027	0.7	13.0	MW	C	N
0.250	6.35	10019	1.00	25.4	.194	4.9	9.0	1.6	.54	14	4.9	22	.34	8.5	0.028	0.7	11.0	MW	C	Z
0.250	6.35	FF-11	1.00	25.4	.190	4.8	8.1	1.4	.49	13	4.0	18	.42	10.7	0.030	0.8	14.0	SST	CG	N
0.250	6.35	M-18	1.00	25.4	.190	4.8	13	2.3	.45	11	6.0	27	.34	8.6	0.030	0.8	10.3	MW	C	Z
0.250	6.35	MM-37	1.00	25.4	.190	4.8	15	2.6	.41	10	6.0	27	.29	7.2	0.030	0.8	9.50	MW	CG	Z
0.250	6.35	3567	1.00	25.4	.188	4.8	18	3.2	.36	9.2	6.6	29	.31	7.9	0.031	0.8	9.00	MW	C	Z
0.250	6.35	A-41	1.00	25.4	.186	4.7	11	2.0	.46	12	5.2	23	.51	13.0	0.032	0.8	15.0	SPR	C	BO
0.250	6.35	QQ-66	1.00	25.4	.186	4.7	22	3.9	.32	8.2	7.2	32	.30	7.7						



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	A10-25	1.03	26.2	.214	5.4	.56	.10	.64	16	.36	1.6	.40	10.1	0.018	0.5	21.0	SST	C	N
0.250	6.35	10179	1.03	26.2	.202	5.1	4.6	.80	.52	13	2.4	11	.26	6.7	0.024	0.6	11.0	HD	CG	N
0.250	6.35	S-999	1.03	26.2	.188	4.8	12	2.1	.36	9.2	4.4	20	.34	8.7	0.031	0.8	11.0	SST	CG	N
0.250	6.35	2621	1.03	26.2	.172	4.4	25	4.4	.35	8.8	8.8	39	.66	16.8	0.039	1.0	16.0	HD	C	Z
0.250	6.35	A15-15	1.05	26.6	.170	4.3	30	5.3	.30	7.5	8.9	39	.59	15.0	0.040	1.0	13.8	SST	C	N
0.250	6.35	YY-3	1.06	27.0	.210	5.3	2.1	.36	.62	16	1.3	5.7	.22	5.6	0.020	0.5	10.0	SST	C	N
0.250	6.35	TT-19	1.06	27.0	.204	5.2	2.5	.45	.72	18	1.8	8.2	.34	8.6	0.023	0.6	13.8	SST	C	N
0.250	6.35	11468	1.06	27.0	.204	5.2	3.5	.61	.55	14	1.9	8.6	.27	6.9	0.023	0.6	10.8	SST	C	N
0.250	6.35	WW-33	1.06	27.0	.202	5.1	3.8	.66	.73	18	2.7	12	.34	8.5	0.024	0.6	13.0	MW	C	N
0.250	6.35	HH-65	1.06	27.0	.186	4.7	13	2.3	.39	10	5.2	23	.42	10.6	0.032	0.8	13.0	SPR	CG	N
0.250	6.35	F-21	1.06	27.0	.184	4.7	16	2.7	.37	9.3	5.7	25	.45	11.5	0.033	0.8	12.8	SPR	C	Z
0.250	6.35	A9-19	1.06	27.0	.178	4.5	15	2.7	.41	11	6.4	28	.65	16.5	0.036	0.9	18.0	SPR	CG	N
0.250	6.35	F-31	1.06	27.0	.156	4.0	88	15	.17	4.3	15	67	.54	13.7	0.047	1.2	11.5	SPR	CG	Z
0.250	6.35	12407	1.09	27.8	.224	5.7	.19	.03	.85	22	.16	.73	.25	6.3	0.013	0.3	18.0	MW	C	N
0.250	6.35	3274	1.09	27.8	.174	4.4	26	4.6	.31	7.9	8.2	36	.53	13.5	0.038	1.0	14.0	SPR	CG	Z
0.250	6.35	AA-35	1.13	28.6	.230	5.8	.04	.01	.85	21	.03	.14	.28	7.1	0.010	0.3	27.0	SST	C	N
0.250	6.35	S-197	1.13	28.6	.222	5.6	.23	.04	.86	22	.20	.89	.26	6.7	0.014	0.4	17.8	SST	C	N
0.250	6.35	2834	1.13	28.6	.216	5.5	1.0	.17	.91	23	.91	4.1	.21	5.4	0.017	0.4	11.5	MW	C	Z
0.250	6.35	2877	1.13	28.6	.216	5.5	.45	.08	.72	18	.32	1.4	.41	10.4	0.017	0.4	23.0	MW	C	Z
0.250	6.35	4288	1.13	28.6	.216	5.5	.50	.09	.75	19	.38	1.7	.37	9.5	0.017	0.4	21.0	MW	C	Z
0.250	6.35	II-5	1.13	28.6	.210	5.3	1.5	.25	.81	20	1.2	5.2	.32	8.1	0.020	0.5	15.0	MW	C	Z
0.250	6.35	1890	1.13	28.6	.200	5.1	4.5	.78	.78	20	3.5	15	.35	8.9	0.025	0.6	13.0	MW	C	Z
0.250	6.35	3561	1.13	28.6	.198	5.0	6.9	1.2	.57	14	3.9	17	.30	7.6	0.026	0.7	10.5	MW	C	Z
0.250	6.35	DD-8	1.13	28.6	.190	4.8	6.5	1.1	.59	15	3.8	17	.54	13.7	0.030	0.8	17.0	SST	C	N
0.250	6.35	S-1156	1.13	28.6	.186	4.7	13	2.2	.38	9.7	4.8	21	.42	10.6	0.032	0.8	12.0	SST	C	N
0.250	6.35	S-975	1.13	28.6	.180	4.6	16	2.8	.38	9.5	6.0	27	.48	12.2	0.035	0.9	13.8	SST	CG	N
0.250	6.35	YY-17	1.13	28.6	.178	4.5	18	3.1	.37	9.3	6.5	29	.50	12.8	0.036	0.9	14.0	SST	CG	N
0.250	6.35	A14-39	1.13	28.6	.174	4.4	24	4.2	.34	8.7	8.2	36	.58	14.7	0.038	1.0	15.3	SPR	CG	N
0.250	6.35	EE-34	1.13	28.6	.150	3.8	93	16	.17	4.3	16	70	.64	16.2	0.050	1.3	12.8	SST	CG	N
0.250	6.35	HH-55	1.16	29.4	.214	5.4	.58	.10	.78	20	.45	2.0	.38	9.6	0.018	0.5	20.0	SST	C	N
0.250	6.35	LL-70	1.16	29.4	.190	4.8	9.9	1.7	.60	15	6.0	27	.39	9.9	0.030	0.8	13.0	MW	CG	N
0.250	6.35	S-322	1.16	29.4	.156	4.0	66	12	.21	5.4	14	63	.61	15.5	0.047	1.2	13.0	SST	CG	N
0.250	6.35	O-102	1.19	30.2	.212	5.4	.89	.16	.81	21	.72	3.2	.38	9.7	0.019	0.5	19.0	MW	C	Z
0.250	6.35	BB-30	1.19	30.2	.170	4.3	27	4.7	.33	8.3	8.9	39	.60	15.2	0.040	1.0	15.0	SST	CG	N
0.250	6.35	L-30	1.23	31.3	.150	3.8	140	25	.12	3.0	17	74	.50	12.7	0.050	1.3	10.0	SPR	CG	Z
0.250	6.35	CC-87	1.25	31.8	.226	5.7	.18	.03	1.1	27	.19	.84	.19	4.7	0.012	0.3	14.5	MW	C	N
0.250	6.35	B2-39	1.25	31.8	.210	5.3	1.6	.28	.95	24	1.5	6.7	.30	7.6	0.020	0.5	14.0	MW	C	N
0.250	6.35	7	1.25	31.8	.204	5.2	3.0	.52	.70	18	2.1	9.3	.33	8.5	0.023	0.6	13.5	HD	C	Z
0.250	6.35	S-138	1.25	31.8	.202	5.1	2.6	.45	.84	21	2.2	9.6	.41	10.4	0.024	0.6	16.0	SST	C	N
0.250	6.35	Y-81	1.25	31.8	.202	5.1	3.2	.56	.87	22	2.8	12	.38	9.8	0.024	0.6	15.0	MW	C	N
0.250	6.35	F-14	1.25	31.8	.198	5.0	4.9	.85	.81	20	3.9	17	.39	9.9	0.026	0.7	14.0	MW	C	Z
0.250	6.35	CC-4	1.25	31.8	.190	4.8	4.8	.83	.50	13	2.4	11	.75	19.1	0.030	0.8	25.0	MW	CG	N
0.250	6.35	A14-3	1.25	31.8	.170	4.3	27	4.8	.35	8.8	9.5	42	.66	16.8	0.040	1.0	16.5	SPR	CG	N
0.250	6.35	S-725	1.25	31.8	.166	4.2	29	5.0	.35	9.0	10	45	.76	19.2	0.042	1.1	17.0	SST	C	N
0.250	6.35	B10-6	1.25	31.8	.162	4.1	39	6.7	.32	8.2	12	55	.79	20.1	0.044	1.1	18.0	SPR	CG	N
0.250	6.35	CC-57	1.28	32.5	.190	4.8	9.9	1.7	.60	15	6.0	27	.39	9.9	0.030	0.8	13.0	MW	CG	Z
0.250	6.35	4296	1.31	33.3	.182	4.6	14	2.5	.44	11	6.2	28	.56	14.2	0.034	0.9	15.5	SPR	C	Z
0.250	6.35	M-148	1.31	33.3	.166	4.2	36	6.2	.31	7.8	11	48	.67	17.1	0.042	1.1	16.0	SPR	CG	Z
0.250	6.35	S-331	1.34	34.1	.214	5.4	1.1	.19	.87	22	.93	4.2	.23	5.9	0.018	0.5	12.0	SST	C	N
0.250	6.35	151-B	1.38	34.9	.210	5.3	2.0	.35	.96	24	1.9	8.5	.25	6.4	0.020	0.5	11.5	MW	C	Z
0.250	6.35	3780	1.38	34.9	.194	4.9	6.0	1.0	.82	21	4.9	22	.46	11.7	0.028	0.7	15.5	MW	C	Z
0.250	6.35	J-47	1.38	34.9	.190	4.8	5.0	.87	.66	17	3.3	14	.72	18.3	0.030	0.8	24.0	MW	CG	Z
0.250	6.35	PP-99	1.38	34.9	.190	4.8	11	1.9	.38	9.6	4.0	18	.36	9.1	0.030	0.8	11.0	SST	C	N
0.250	6.35	201-B	1.38	34.9	.180	4.6	15	2.6	.60	15	8.9	40	.61	15.6	0.035	0.9	16.5	MW	C	Z
0.250	6.35	II-66	1.38	34.9	.170	4.3	27	4.8	.35	8.8	9.5	42	.70	17.8	0.040	1.0	16.5	SPR	C	Z
0.250	6.35	S-1023	1.38	34.9	.160	4.1	44	7.7	.28	7.2	12	55	.70	17.7	0.045	1.1	15.5	SST	CG	N
0.250	6.35	10877	1.41	35.7	.210	5.3	1.0	.18	1.0	25	1.0	4.5	.41	10.4	0.020	0.5	20.5	MW	CG	N
0.250	6.35	2980	1.41	35.7	.210	5.3	1.3	.23	1.1	27	1.4	6.3	.35	8.8	0.020	0.5	16.3	MW	C	Z



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.250	6.35	G-96	1.75	44.5	.210	5.3	1.4	.24	1.4	36	1.9	8.5	.34	8.6	0.020	0.5	16.0	MW	C	N
0.250	6.35	12620	1.75	44.5	.200	5.1	2.3	.41	1.2	29	2.7	12	.60	15.2	0.025	0.6	23.0	MW	C	N
0.250	6.35	B2-4	1.75	44.5	.200	5.1	4.7	.82	.74	19	3.5	16	.34	8.6	0.025	0.6	12.5	MW	CL	N
0.250	6.35	11349	1.75	44.5	.190	4.8	3.3	.58	.81	20	2.6	12	.95	24.0	0.030	0.8	31.5	SST	CG	N
0.250	6.35	J-61	1.75	44.5	.182	4.6	8.7	1.5	.71	18	6.2	28	.82	20.7	0.034	0.9	24.0	SPR	C	Z
0.250	6.35	201-C	1.75	44.5	.180	4.6	12	2.0	.77	20	8.9	40	.76	19.3	0.035	0.9	20.8	MW	C	Z
0.250	6.35	A12-18	1.78	45.2	.200	5.1	2.3	.40	1.2	30	2.7	12	.61	15.6	0.025	0.6	23.5	MW	C	N
0.250	6.35	1941	1.78	45.2	.182	4.6	10	1.8	.60	15	6.2	28	.73	18.6	0.034	0.9	20.5	SPR	C	Z
0.250	6.35	2746	1.78	45.2	.176	4.5	15	2.7	.68	17	10	47	.78	19.7	0.037	0.9	20.0	MW	C	Z
0.250	6.35	10937	1.78	45.2	.170	4.3	19	3.3	.51	13	9.5	42	.93	23.6	0.040	1.0	23.3	SPR	CG	N
0.250	6.35	3005	1.81	46.0	.174	4.4	17	3.0	.47	12	8.2	36	.81	20.5	0.038	1.0	20.3	SPR	C	Z
0.250	6.35	11109	1.88	47.6	.210	5.3	1.1	.18	1.5	37	1.5	6.8	.42	10.7	0.020	0.5	20.0	MW	C	Z
0.250	6.35	10860	1.88	47.6	.188	4.8	5.3	.93	1.0	27	5.6	25	.83	21.1	0.031	0.8	25.8	MW	C	BO
0.250	6.35	F-61	1.94	49.2	.142	3.6	83	15	.25	6.3	21	92	1.16	29.5	0.054	1.4	21.5	SPR	CG	Z
0.250	6.35	3730	2.00	50.8	.216	5.5	.68	.12	1.7	43	1.2	5.2	.29	7.3	0.017	0.4	16.0	MW	C	GI
0.250	6.35	2566	2.00	50.8	.214	5.4	.55	.10	1.6	39	.85	3.8	.45	11.4	0.018	0.5	24.0	MW	C	Z
0.250	6.35	B2-45	2.00	50.8	.206	5.2	2.3	.40	1.1	28	2.5	11	.34	8.7	0.022	0.6	14.5	MW	C	Z
0.250	6.35	10191	2.00	50.8	.200	5.1	2.7	.48	1.3	32	3.5	16	.53	13.3	0.025	0.6	20.0	MW	C	Z
0.250	6.35	4251	2.00	50.8	.200	5.1	1.9	.33	1.3	32	2.4	11	.73	18.4	0.025	0.6	28.0	MW	C	Z
0.250	6.35	3511	2.00	50.8	.198	5.0	2.7	.47	1.4	34	3.6	16	.65	16.5	0.026	0.7	24.0	MW	C	Z
0.250	6.35	A14-35	2.00	50.8	.178	4.5	11	1.9	.64	16	7.0	31	.89	22.6	0.036	0.9	24.8	SPR	CG	N
0.250	6.35	L-60	2.02	51.2	.170	4.3	17	2.9	.57	15	9.5	42	1.04	26.4	0.040	1.0	26.0	SPR	CG	Z
0.250	6.35	S-3183	2.13	54.0	.168	4.3	14	2.4	.70	18	9.5	42	1.25	31.8	0.041	1.0	30.5	SST	CG	N
0.250	6.35	10430	2.22	56.4	.180	4.6	16	2.7	.42	11	6.4	29	.60	15.1	0.035	0.9	16.0	SPR	C	Z
0.250	6.35	F-99	2.25	57.2	.192	4.9	3.1	.55	1.3	33	4.1	18	.96	24.3	0.029	0.7	32.0	MW	C	Z
0.250	6.35	O-43	2.34	59.5	.192	4.9	4.3	.75	1.3	32	5.4	24	.73	18.4	0.029	0.7	24.0	MW	C	N
0.250	6.35	B10-41	2.38	60.3	.200	5.1	3.8	.66	.92	23	3.5	16	.40	10.2	0.025	0.6	15.0	MW	C	Z
0.250	6.35	4119	2.50	63.5	.190	4.8	4.7	.81	1.3	33	6.0	27	.80	20.2	0.030	0.8	25.5	MW	C	Z
0.250	6.35	00-56	2.66	67.5	.170	4.3	12	2.1	.77	20	9.5	42	1.38	35.1	0.040	1.0	34.5	SPR	CG	BO
0.250	6.35	O-55	2.69	68.2	.202	5.1	2.0	.35	1.7	42	3.3	15	.57	14.5	0.024	0.6	22.8	MW	C	Z
0.250	6.35	A-79	2.75	69.9	.194	4.9	4.0	.71	1.2	31	4.9	22	.64	16.4	0.028	0.7	22.0	MW	C	N
0.250	6.35	LL-17	2.78	70.6	.190	4.8	2.6	.46	1.4	36	3.7	17	1.35	34.3	0.030	0.8	44.0	MW	C	N
0.250	6.35	W-55	3.00	76.2	.166	4.2	17	2.9	.66	17	11	48	1.39	35.2	0.042	1.1	32.0	SPR	C	Z
0.250	6.35	11477	3.03	77.0	.160	4.1	22	3.9	.60	15	13	59	1.53	38.9	0.045	1.1	33.0	SPR	CG	Z
0.250	6.35	12743	3.13	79.4	.178	4.5	5.6	.98	1.2	32	7.0	31	1.69	43.0	0.036	0.9	46.0	SPR	C	N
0.250	6.35	12505	3.38	85.7	.170	4.3	9.5	1.7	1.0	25	9.5	42	1.80	45.7	0.040	1.0	44.0	SPR	C	N
0.250	6.35	S-1001	3.75	95.3	.198	5.0	.91	.16	2.2	56	2.0	8.9	1.53	39.0	0.026	0.7	58.0	SST	C	N
0.250	6.35	S-1504	4.00	101.6	.200	5.1	.73	.13	2.5	62	1.8	7.9	1.55	39.4	0.025	0.6	61.0	SST	C	N
0.250	6.35	2822	4.75	120.7	.170	4.3	6.3	1.1	1.5	38	9.5	42	2.60	66.0	0.040	1.0	65.0	SPR	CG	GI
0.250	6.35	3946	4.88	123.8	.180	4.6	3.4	.59	1.9	48	6.4	29	2.31	58.7	0.035	0.9	66.0	SPR	CG	GI
0.250	6.35	B10-55	4.88	123.8	.174	4.4	4.8	.85	1.7	43	8.2	36	2.55	64.7	0.038	1.0	67.0	SPR	CG	Z
0.250	6.35	12708	6.50	165.1	.178	4.5	2.5	.44	2.9	73	7.2	32	3.64	92.4	0.036	0.9	100.0	MW	C	N
0.262	6.65	12798	.86	21.8	.166	4.2	80	14	.27	6.8	21	94	.56	14.3	0.048	1.2	11.8	MW	CG	N
0.266	6.76	W-46	.19	4.8	.232	5.9	5.2	.92	.11	2.8	.59	2.6	.08	1.9	0.017	0.4	3.50	MW	C	Z
0.266	6.76	J-77	.22	5.6	.176	4.5	277	48	.04	.99	11	48	.18	4.6	0.045	1.1	4.00	SPR	CG	N
0.266	6.76	EE-27	.28	7.1	.236	6.0	1.4	.24	.19	4.9	.26	1.2	.09	2.3	0.015	0.4	5.00	SST	C	N
0.266	6.76	B5-63	.31	7.9	.246	6.2	.17	.03	.23	5.9	.04	.18	.08	2.0	0.010	0.3	7.00	MW	C	N
0.266	6.76	CC-52	.31	7.9	.220	5.6	10	1.8	.18	4.6	1.9	8.3	.13	3.4	0.023	0.6	4.75	MW	C	N
0.266	6.76	O-27	.31	7.9	.206	5.2	45	7.9	.13	3.2	5.6	25	.15	3.8	0.030	0.8	4.00	MW	C	N
0.266	6.76	S-1389	.31	7.9	.206	5.2	31	5.5	.12	3.1	3.8	17	.17	4.2	0.030	0.8	4.50	SST	C	N
0.266	6.76	I-84	.31	7.9	.196	5.0	59	10	.10	2.6	6.1	27	.18	4.4	0.035	0.9	5.00	SPR	CG	Z
0.266	6.76	U-72	.34	8.7	.206	5.2	30	5.2	.19	4.8	5.6	25	.15	3.8	0.030	0.8	5.00	MW	CG	N
0.266	6.76	EE-26	.38	9.5	.214	5.4	8.4	1.5	.19	4.9	1.6	7.2	.18	4.6	0.026	0.7	7.00	SST	CG	N
0.266	6.76	Y-5	.38	9.5	.210	5.3	19	3.4	.16	4.1	3.1	14	.14	3.6	0.028	0.7	5.00	SST	CG	N
0.266	6.76	S-1112	.38	9.5	.202	5.1	35	6.0	.13	3.4	4.6	20	.16	4.1	0.032	0.8	5.00	SST	CG	N
0.266	6.76	S-815	.38	9.5	.160	4.1	345	60	.05	1.3	18	78	.27	6.7	0.053	1.3	5.00	SST	CG	N
0.266	6.76	B2-38	.39	9.9	.210	5.3	22	3.8	.21	5.4	4.6	20	.17	4.3	0.028	0.7	5.00	MW	C	N
0.266	6.76	FF-5	.44	11.1	.242	6.1	.20	.04	.31	7.8	.06	.27	.13	3.4	0.012	0.3	10.0	SST	C	N
0.266	6.76	10790	.44	11.1	.206	5.2	20	3.4	.19	4.9	3.8	17	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.266	6.76	A9-6	.44	11.1	.184	4.7	90	16	.11	2.7	9.6	43	.25	6.2	0.041	1.0	6.00	SPR	CG	N
0.266	6.76	NN-43	.44	11.1	.184	4.7	58	10	.13	3.3	7.6	34	.31	7.8	0.041	1.0	7.50	SST	CG	N
0.266	6.76	12032	.47	11.9	.240	6.1	.53	.09	.37	9.3	.20	.87	.10	2.6	0.013	0.3	6.75	MW	C	N
0.266	6.76	KK-45	.47	11.9	.230	5.8	2.0	.35	.32	8.2	.65	2.9	.14	3.7	0.018	0.5	7.00	MW	C	Z
0.266	6.76	3416	.47	11.9	.226	5.7	3.1	.55	.31	7.8	.96	4.3	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.266	6.76	3232	.47	11.9	.214	5.4	19	3.4	.19	4.9	3.7	16	.14	3.6	0.026	0.7	4.50	MW	C	Z
0.266	6.76	S-1024	.47	11.9	.204	5.2	31	5.4	.14	3.4	4.2	18	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.266	6.76	S-1484	.47	11.9	.196	5.0	77	13	.07	1.9	5.7	25	.18	4.4	0.035	0.9	4.00	SST	C	N
0.266	6.76	I-36	.50	12.7	.226	5.7	3.2	.56	.36	9.0	1.1	5.1	.15	3.7	0.020	0.5	6.25	SST	C	N
0.266	6.76	L-																		



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.266	6.76	W-14	.50	12.7	.146	3.7	376	66	.07	1.7	25	111	.42	10.7	0.060	1.5	7.00	SST	CG	N
0.266	6.76	NN-49	.50	12.7	.142	3.6	491	86	.06	1.4	27	121	.40	10.2	0.062	1.6	6.50	SST	CG	N
0.266	6.76	O-146	.53	13.5	.202	5.1	26	4.5	.18	4.5	4.6	20	.19	4.9	0.032	0.8	6.00	SST	CG	N
0.266	6.76	UU-40	.53	13.5	.202	5.1	24	4.2	.21	5.2	4.9	22	.26	6.5	0.032	0.8	7.00	SPR	C	N
0.266	6.76	N-62	.53	13.5	.196	5.0	30	5.2	.21	5.2	6.1	27	.28	7.1	0.035	0.9	8.00	SPR	CG	N
0.266	6.76	B-53	.53	13.5	.180	4.6	95	17	.12	3.0	11	49	.29	7.4	0.043	1.1	6.75	SPR	CG	Z
0.266	6.76	A-73	.56	14.3	.238	6.0	.87	.15	.46	12	.41	1.8	.10	2.5	0.014	0.4	6.00	MW	C	GI
0.266	6.76	JJ-45	.56	14.3	.210	5.3	8.2	1.4	.28	7.2	2.3	10	.28	7.1	0.028	0.7	9.00	SST	C	N
0.266	6.76	JJ-91	.56	14.3	.210	5.3	9.5	1.7	.28	7.2	2.7	12	.28	7.1	0.028	0.7	9.00	MW	C	N
0.266	6.76	3713	.56	14.3	.202	5.1	24	4.2	.29	7.3	6.8	30	.22	5.7	0.032	0.8	7.00	MW	CG	Z
0.266	6.76	A11-60	.56	14.3	.202	5.1	17	2.9	.27	6.9	4.6	20	.27	6.8	0.032	0.8	8.33	SST	CG	N
0.266	6.76	L-85	.56	14.3	.192	4.9	41	7.2	.17	4.4	7.2	32	.28	7.0	0.037	0.9	7.50	SPR	CG	Z
0.266	6.76	B11-33	.59	15.1	.230	5.8	.82	.14	.34	8.7	.28	1.3	.25	6.4	0.018	0.5	14.0	MW	CG	N
0.266	6.76	A10-35	.59	15.1	.204	5.2	20	3.6	.20	5.2	4.2	18	.23	5.9	0.031	0.8	6.50	SST	C	N
0.266	6.76	O-143	.59	15.1	.186	4.7	70	12	.12	3.0	8.4	37	.28	7.1	0.040	1.0	6.00	SST	C	N
0.266	6.76	II-99	.59	15.1	.172	4.4	150	26	.09	2.3	13	59	.28	7.2	0.047	1.2	6.00	SST	CG	N
0.266	6.76	H-27	.63	15.9	.208	5.3	13	2.3	.39	10	5.1	23	.23	5.9	0.029	0.7	8.00	MW	CG	N
0.266	6.76	S-156	.63	15.9	.204	5.2	30	5.3	.14	3.5	4.2	18	.19	4.7	0.031	0.8	5.00	SST	C	N
0.266	6.76	B8-34	.66	16.7	.212	5.4	9.0	1.6	.31	7.8	2.8	12	.20	5.1	0.027	0.7	7.50	SST	CG	N
0.266	6.76	3568	.66	16.7	.208	5.3	13	2.3	.40	10	5.1	23	.26	6.6	0.029	0.7	8.00	MW	C	Z
0.266	6.76	UU-37	.66	16.7	.186	4.7	35	6.1	.24	6.1	8.4	37	.40	10.2	0.040	1.0	10.0	SST	CG	N
0.266	6.76	N-12	.69	17.4	.248	6.3	.05	.01	.57	15	.03	.13	.11	2.9	0.009	0.2	11.8	SST	C	N
0.266	6.76	A13-51	.69	17.4	.238	6.0	.25	.04	.45	11	.11	.50	.24	6.0	0.014	0.4	16.0	SPR	C	N
0.266	6.76	II-88	.69	17.4	.216	5.5	3.5	.62	.36	9.2	1.3	5.7	.33	8.3	0.025	0.6	12.0	SST	C	N
0.266	6.76	B11-52	.69	17.4	.208	5.3	13	2.2	.40	10	5.1	23	.23	5.9	0.029	0.7	8.00	MW	CG	N
0.266	6.76	10897	.69	17.4	.184	4.7	61	11	.15	3.8	9.0	40	.30	7.6	0.041	1.0	7.25	SST	CG	N
0.266	6.76	A9-64	.69	17.4	.180	4.6	72	13	.14	3.6	10	46	.32	8.1	0.043	1.1	7.50	SST	CG	N
0.266	6.76	L-90	.69	17.4	.168	4.3	127	22	.13	3.2	16	71	.42	10.6	0.049	1.2	8.50	SPR	CG	GI
0.266	6.76	HH-71	.72	18.2	.184	4.7	40	7.0	.24	6.1	9.6	43	.45	11.5	0.041	1.0	11.0	SPR	CG	GI
0.266	6.76	3104	.75	19.1	.238	6.0	.58	.10	.62	16	.36	1.6	.13	3.2	0.014	0.4	8.00	MW	C	Z
0.266	6.76	A-50	.75	19.1	.236	6.0	.29	.05	.47	12	.14	.60	.29	7.2	0.015	0.4	18.0	MW	C	Z
0.266	6.76	A-28	.75	19.1	.226	5.7	1.3	.23	.49	12	.64	2.9	.27	6.7	0.020	0.5	12.3	SST	C	N
0.266	6.76	A-72	.75	19.1	.216	5.5	5.1	.89	.50	13	2.5	11	.25	6.4	0.025	0.6	10.0	MW	CG	Z
0.266	6.76	4292	.75	19.1	.212	5.4	5.2	.90	.40	10	2.1	9.1	.35	8.9	0.027	0.7	13.0	MW	CG	Z
0.266	6.76	Y-76	.75	19.1	.206	5.2	9.8	1.7	.39	9.8	3.8	17	.30	7.6	0.030	0.8	10.0	SST	CG	N
0.266	6.76	A15-22	.75	19.1	.202	5.1	12	2.1	.39	9.9	4.6	20	.35	8.9	0.032	0.8	11.0	SST	CG	N
0.266	6.76	S-211	.75	19.1	.196	5.0	17	3.0	.33	8.4	5.7	25	.39	9.8	0.035	0.9	11.0	SST	CG	N
0.266	6.76	FF-28	.81	20.6	.222	5.6	3.4	.59	.59	15	2.0	8.8	.22	5.6	0.022	0.6	9.00	MW	C	Z
0.266	6.76	Q-66	.81	20.6	.220	5.6	6.2	1.1	.29	7.4	1.8	8.1	.16	4.1	0.023	0.6	6.00	SST	C	N
0.266	6.76	S-907	.81	20.6	.198	5.0	19	3.4	.28	7.1	5.4	24	.31	7.8	0.034	0.9	9.00	SST	CG	N
0.266	6.76	LL-46	.84	21.4	.222	5.6	2.2	.39	.57	15	1.3	5.6	.27	6.8	0.022	0.6	11.3	SST	C	N
0.266	6.76	N-128	.84	21.4	.206	5.2	20	3.4	.29	7.3	5.6	25	.23	5.7	0.030	0.8	6.50	MW	C	Z
0.266	6.76	VV-17	.88	22.2	.236	6.0	.31	.05	.64	16	.20	.88	.24	6.1	0.015	0.4	15.0	SST	C	N
0.266	6.76	Y-72	.88	22.2	.196	5.0	22	3.9	.27	7.0	6.1	27	.39	9.8	0.035	0.9	10.0	SPR	C	N
0.266	6.76	S-1585	.88	22.2	.184	4.7	29	5.0	.31	8.0	9.0	40	.53	13.5	0.041	1.0	13.0	SST	CG	N
0.266	6.76	XX-67	.88	22.2	.180	4.6	37	6.6	.27	6.9	10	45	.60	15.3	0.043	1.1	14.0	SPR	CG	Z
0.266	6.76	S-1527	.88	22.2	.176	4.5	51	8.9	.23	5.9	12	52	.56	14.3	0.045	1.1	11.5	SST	C	N
0.266	6.76	3774	.94	23.8	.216	5.5	2.9	.51	.54	14	1.6	6.9	.40	10.2	0.025	0.6	16.0	MW	CG	Z
0.266	6.76	3732	.94	23.8	.192	4.9	19	3.3	.38	9.6	7.2	32	.52	13.2	0.037	0.9	14.0	SPR	CG	Z
0.266	6.76	NN-71	.94	23.8	.146	3.7	251	44	.11	2.7	26	118	.63	16.0	0.060	1.5	10.5	SPR	CG	N
0.266	6.76	00-9	.97	24.6	.206	5.2	7.1	1.3	.53	13	3.8	17	.39	9.9	0.030	0.8	13.0	SST	CG	N
0.266	6.76	AA-41	1.00	25.4	.226	5.7	1.5	.26	.73	19	1.1	4.8	.27	6.9	0.020	0.5	12.5	MW	C	Z
0.266	6.76	KK-65	1.00	25.4	.208	5.3	8.1	1.4	.63	16	5.1	23	.36	9.2	0.029	0.7	11.5	MW	C	Z
0.266	6.76	L-43	1.00	25.4	.206	5.2	13	2.2	.44	11	5.6	25	.30	7.6	0.030	0.8	9.00	MW	C	Z
0.266	6.76	S-203	1.00	25.4	.202	5.1	9.4	1.6	.48	12	4.6	20	.45	11.4	0.032	0.8	13.0	SST	C	N
0.266	6.76	2895	1.00	25.4	.198	5.0	14	2.5	.56	14	7.9	35	.44	11.2	0.034	0.9	13.0	MW	CG	Z
0.266	6.76	JJ-69	1.00	25.4	.166	4.2	105	18	.15	3.8	16	71	.53	13.3	0.050	1.3	10.5	SPR	CG	N
0.266	6.76	12586	1.03	26.2	.216	5.5	3.3	.59	.66	17	2.2	9.8	.38	9.5	0.025	0.6	14.0	MW	C	Z
0.266	6.76	10537	1.03	26.2	.202	5.1	9.8	1.7	.58	15	5.7	25	.45	11.4	0.032	0.8	14.0	MW	CG	Z
0.266	6.76	B7-19	1.06	27.0	.210	5.3	5.7	1.0	.68	17	3.9	17	.38	9.6	0.028	0.7	13.5	MW	CG	N
0.266	6.76	A9-58	1.06	27.0	.204	5.2	6.8	1.2	.55	14	3.7	17	.51	13.0	0.031	0.8	15.5	SST	C	N
0.266	6.76	S-1151	1.06	27.0	.190	4.8	17	3.0	.42	11	7.2	32	.57	14.5	0.038	1.0	15.0	SST	CG	N
0.266	6.76	A15-28	1.09	27.8	.194	4.9	15	2.6	.44	11	6.6	29	.59	15.1	0.036	0.9	15.5	SPR	C	Z
0.266	6.76	N-43	1.13	28.6	.236	6.0	.31	.05	.89	22	.28	1.2	.24	6.1	0.015	0.4	15.0	SST	C	N
0.266	6.76	4195	1.13	28.6	.228	5.8	.90	.16	.80	20	.72	3.2	.32	8.2	0.019	0.5	16.0	MW	C	Z
0.266	6.76	VV-14	1.13	28.6	.220	5.6	2.9	.51	.63	16	1.8	8.1	.26	6.7	0.023	0.6	10.5	SST	C	N
0.266	6.76	2523	1.13	28.6	.208	5.3	5.7	.99	.65	16	3.7	16	.48	12.2	0.029	0.7	15.5	MW	C	Z
0.266	6.76	10350	1.13	28.6	.176	4.5	44	7.7	.29	7.3	13	56	.65	16.6	0.045	1.1	14.5	SPR	CG	N
0.266	6.76	B7-12	1.13	28.6	.176	4.5	38	6.7	.33	8.3	13	56	.73	18.6	0.045	1.1	16.3	SPR	CG	N
0.266	6.76	EE-43	1.13	28.6	.166															



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.266	6.76	M-26	1.38	34.9	.236	6.0	.38	.07	1.2	29	.44	2.0	.23	5.7	0.015	0.4	14.0	MW	C	Z
0.266	6.76	VV-59	1.38	34.9	.232	5.9	.79	.14	1.2	29	.91	4.0	.22	5.6	0.017	0.4	12.0	MW	C	Z
0.266	6.76	3264	1.38	34.9	.206	5.2	4.3	.75	.66	17	2.8	12	.72	18.3	0.030	0.8	23.0	MW	C	Z
0.266	6.76	3844	1.38	34.9	.206	5.2	3.9	.68	.60	15	2.3	10	.78	19.8	0.030	0.8	25.0	MW	C	N
0.266	6.76	S-1494	1.38	34.9	.170	4.3	39	6.8	.37	9.3	14	63	.90	22.9	0.048	1.2	18.8	SST	CG	N
0.266	6.76	10952	1.41	35.7	.184	4.7	28	4.9	.34	8.7	9.6	43	.65	16.4	0.041	1.0	14.8	SPR	C	N
0.266	6.76	12418	1.44	36.5	.218	5.5	3.1	.54	1.1	28	3.16	14.1	.34	8.5	0.024	0.6	13.0	MW	C	N
0.266	6.76	YY-57	1.44	36.5	.200	5.1	11	2.0	.47	12	5.4	24	.50	12.6	0.033	0.8	14.0	SPR	C	Z
0.266	6.76	11191	1.47	37.3	.186	4.7	24	4.2	.37	9.5	9.0	40	.65	16.5	0.040	1.0	15.3	SPR	C	Z
0.266	6.76	11418	1.50	38.1	.186	4.7	25	4.3	.37	9.3	9.0	40	.64	16.3	0.040	1.0	15.0	SPR	C	Z
0.266	6.76	2886	1.53	38.9	.200	5.1	8.0	1.4	.67	17	5.4	24	.53	13.4	0.033	0.8	16.0	SPR	CG	GI
0.266	6.76	1515	1.53	38.9	.196	5.0	12	2.2	.69	17	8.4	37	.57	14.5	0.035	0.9	16.3	MW	CG	GI
0.266	6.76	S-1354	1.56	39.7	.204	5.2	6.9	1.2	.60	15	4.2	18	.50	12.6	0.031	0.8	15.0	SST	C	N
0.266	6.76	3198	1.56	39.7	.202	5.1	9.2	1.6	.74	19	6.8	30	.51	13.0	0.032	0.8	15.0	MW	C	Z
0.266	6.76	NN-33	1.63	41.3	.222	5.6	1.3	.22	1.2	31	1.6	7.0	.40	10.1	0.022	0.6	18.0	SST	CG	N
0.266	6.76	3528	1.69	42.8	.212	5.4	2.0	.34	.85	22	1.7	7.4	.84	21.3	0.027	0.7	31.0	MW	CG	Z
0.266	6.76	2530	1.78	45.2	.220	5.6	.73	.13	.83	21	.60	2.7	.96	24.3	0.023	0.6	40.5	MW	C	Z
0.266	6.76	B11-56	1.88	47.6	.204	5.2	6.8	1.2	.91	23	6.2	28	.56	14.2	0.031	0.8	17.0	MW	C	Z
0.266	6.76	10043	1.88	47.6	.196	5.0	18	3.1	.34	8.7	6.1	27	.46	11.6	0.035	0.9	12.0	SPR	C	Z
0.266	6.76	A10-2	1.88	47.6	.170	4.3	88	15	.17	4.4	15	67	.50	12.8	0.048	1.2	10.5	SPR	CG	N
0.266	6.76	DD-66	1.94	49.2	.192	4.9	7.6	1.3	.88	22	6.7	30	1.04	26.3	0.037	0.9	28.0	SST	CG	N
0.266	6.76	3300	2.00	50.8	.210	5.3	3.7	.65	1.2	32	4.6	20	.59	14.9	0.028	0.7	20.0	MW	C	Z
0.266	6.76	3784	2.00	50.8	.190	4.8	9.9	1.7	.78	20	7.7	34	1.10	28.0	0.038	1.0	28.0	SPR	C	Z
0.266	6.76	10755	2.06	52.4	.192	4.9	7.7	1.3	.88	22	6.7	30	1.07	27.3	0.037	0.9	28.0	SST	C	N
0.266	6.76	10892	2.13	54.0	.222	5.6	1.0	.18	1.5	39	1.6	7.1	.48	12.3	0.022	0.6	22.0	SST	CG	N
0.266	6.76	YY-52	2.13	54.0	.176	4.5	25	4.4	.47	12	12	52	.99	25.1	0.045	1.1	21.0	SST	C	N
0.266	6.76	U-44	2.25	57.2	.214	5.4	1.9	.32	1.5	38	2.8	12	.75	19.2	0.026	0.7	28.0	MW	C	Z
0.266	6.76	K-91	2.25	57.2	.158	4.0	52	9.1	.38	9.6	20	88	1.46	37.0	0.054	1.4	27.0	SPR	CG	Z
0.266	6.76	II-28	2.28	57.9	.166	4.2	24	4.2	.53	13	13	57	1.75	44.5	0.050	1.3	35.0	SST	CG	N
0.266	6.76	3312	2.31	58.7	.212	5.4	2.5	.43	1.6	41	4.0	18	.70	17.8	0.027	0.7	25.0	MW	C	Z
0.266	6.76	00-5	2.31	58.7	.146	3.7	77	14	.34	8.7	26	118	1.77	45.0	0.060	1.5	29.5	SPR	CG	Z
0.266	6.76	3915	2.50	63.5	.190	4.8	9.0	1.6	.86	22	7.7	34	1.20	30.4	0.038	1.0	30.5	SPR	C	Z
0.266	6.76	11462	3.00	76.2	.190	4.8	9.0	1.6	1.2	30	11	48	1.14	29.0	0.038	1.0	30.0	MW	CG	Z
0.266	6.76	UU-55	4.00	101.6	.212	5.4	.88	.15	2.4	61	2.1	9.4	1.59	40.5	0.027	0.7	58.0	SST	C	N
0.266	6.76	10435	4.06	103.2	.184	4.7	7.9	1.4	1.2	31	9.6	43	1.93	48.9	0.041	1.0	47.0	SPR	CG	N
0.275	6.99	A16-69	.94	23.8	.177	4.5	80	14	.27	6.9	22	96	.54	13.7	0.049	1.2	11.0	MW	CG	Z
0.281	7.14	10688	.22	5.6	.231	5.9	33	5.9	.09	2.4	3.1	14	.10	2.5	0.025	0.6	3.00	MW	C	N
0.281	7.14	10684	.25	6.4	.221	5.6	29	5.1	.09	2.3	2.7	12	.16	4.0	0.030	0.8	4.25	SST	C	N
0.281	7.14	12653	.25	6.4	.221	5.6	49	8.6	.11	2.8	5.4	24	.14	3.4	0.030	0.8	3.50	MW	C	N
0.281	7.14	00-62	.25	6.4	.217	5.5	49	8.5	.10	2.4	4.7	21	.13	3.3	0.032	0.8	4.00	SPR	CG	N
0.281	7.14	DD-26	.28	7.1	.217	5.5	22	3.8	.09	2.3	1.9	8.6	.19	4.9	0.032	0.8	6.00	SST	CG	N
0.281	7.14	VV-63	.28	7.1	.211	5.4	72	13	.08	2.0	5.8	26	.18	4.4	0.035	0.9	4.00	SPR	C	Z
0.281	7.14	A9-56	.31	7.9	.257	6.5	.34	.06	.22	5.6	.08	.34	.09	2.3	0.012	0.3	6.50	MW	C	N
0.281	7.14	L-83	.31	7.9	.229	5.8	11	2.0	.18	4.6	2.1	9.3	.13	3.3	0.026	0.7	5.00	SST	CG	N
0.281	7.14	11439	.34	8.7	.221	5.6	29	5.1	.12	3.1	3.6	16	.16	4.0	0.030	0.8	4.25	SST	C	N
0.281	7.14	933	.38	9.5	.201	5.1	75	13	.11	2.9	8.5	38	.26	6.6	0.040	1.0	5.50	HD	C	Z
0.281	7.14	VW-46	.38	9.5	.175	4.4	319	56	.06	1.4	18	80	.27	6.7	0.053	1.3	5.00	SPR	CG	Z
0.281	7.14	930	.38	9.5	.173	4.4	348	61	.05	1.3	18	79	.32	8.2	0.054	1.4	5.00	HD	C	Z
0.281	7.14	I-72	.38	9.5	.131	3.3	2601	456	.02	.43	44	196	.30	7.6	0.075	1.9	4.00	SPR	CG	N
0.281	7.14	II-51	.41	10.3	.249	6.3	.68	.12	.25	6.5	.17	.77	.15	3.9	0.016	0.4	8.50	SST	C	N
0.281	7.14	10744	.41	10.3	.225	5.7	18	3.2	.24	6.0	4.3	19	.17	4.3	0.028	0.7	5.00	MW	C	N
0.281	7.14	Z-13	.41	10.3	.211	5.4	32	5.5	.17	4.4	5.4	24	.21	5.3	0.035	0.9	6.00	SST	C	N
0.281	7.14	NN-17	.41	10.3	.147	3.7	985	173	.03	.89	34	153	.34	8.5	0.067	1.7	5.00	SPR	CG	Z
0.281	7.14	J-12	.41	10.3	.139	3.5	1315	230	.03	.74	38	170	.36	9.0	0.071	1.8	5.00	SPR	CG	N
0.281	7.14	MM-61	.44	11.1	.251	6.4	.34	.06	.24	6.2	.08	.36	.20	5.0	0.015	0.4	12.0	SST	C	N
0.281	7.14	NN-14	.44	11.1	.243	6.2	1.6	.29	.28	7.0	.46	2.0	.16	4.1	0.019	0.5	7.50	SST	C	N
0.281	7.14	2913	.44	11.1	.211	5.4	48	8.5	.12	3.0	5.8	26	.21	5.3	0.035	0.9	5.00	SPR	C	Z
0.281	7.14	EE-13	.44	11.1	.211	5.4	36	6.3	.15	3.8	5.4	24	.19	4.9	0.035	0.9	5.50	SST	CG	N
0.281	7.14	RR-56	.44	11.1	.209	5.3	41	7.2	.15	3.9	6.3	28	.25	6.4	0.036	0.9	6.00	SPR	C	Z
0.281	7.14	3900	.44	11.1	.201	5.1	66	12	.13	3.3	8.5	38	.28	7.1	0.040	1.0	6.00	SPR	C	Z
0.281	7.14	AA-20	.44	11.1	.201	5.1	47	8.2	.16	4.0	7.4	33	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.281	7.14	B-79	.44	11.1	.187	4.7	136	24	.09	2.4	13	57	.26	6.6	0.047	1.2	5.50	SST	CG	N
0.281	7.14	S-1058	.44	11.1	.173	4.4	260	45	.07	1.7	18	79	.30	7.5	0.054	1.4	5.50	SST	CG	N
0.281	7.14	A9-1	.47	11.9	.237	6.0	2.3	.40	.26	6.6	.59	2.6	.21	5.3	0.022	0.6	9.50	SST	CG	N
0.281	7.14	DD-18	.47	11.9	.217	5.5	9.6	1.7	.08	2.1	.81	3.6	.38	9.8	0.032	0.8	11.0	SST	C	N
0.281	7.14	10945	.47	11.9	.215	5.5	37	6.5	.19	4.8	7.1	31	.20	5.0	0.033	0.8	5.00	MW	C	Z
0.281	7.14	A-63	.47	11.9	.203	5.2	78	14	.10	2.6	7.9	35	.20	5.0	0.039	1.0	5.00	SPR	CG	Z
0.281	7.14	J-66	.47	11.9	.189	4.8	104	18	.12	3.1	13	57	.31	7.9	0.046	1.2	6.75	SPR	CG	N
0.281	7.14	W-87	.50	12.7																



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.281	7.14	B2-37	.55	13.9	.201	5.1	46	8.0	.17	4.4	8.0	36	.32	8.1	0.040	1.0	7.00	SST	C	N
0.281	7.14	S-1078	.56	14.3	.231	5.9	9.7	1.7	.22	5.5	2.1	9.3	.15	3.8	0.025	0.6	14.0	SST	C	N
0.281	7.14	3467	.56	14.3	.229	5.8	13	2.3	.19	4.9	2.5	11	.13	3.3	0.026	0.7	5.00	HD	CG	Z
0.281	7.14	A9-50	.56	14.3	.219	5.6	19	3.3	.31	7.9	5.9	26	.23	5.9	0.031	0.8	6.50	MW	C	GI
0.281	7.14	LL-21	.56	14.3	.219	5.6	21	3.7	.28	7.0	5.9	26	.22	5.5	0.031	0.8	6.00	MW	C	N
0.281	7.14	DD-36	.56	14.3	.205	5.2	30	5.3	.23	5.8	6.9	31	.30	7.7	0.038	1.0	8.00	SST	CG	N
0.281	7.14	K-6	.56	14.3	.201	5.1	66	12	.13	3.3	8.5	38	.24	6.1	0.040	1.0	6.00	SPR	CG	Z
0.281	7.14	Q-13	.56	14.3	.187	4.7	100	17	.14	3.5	14	60	.35	9.0	0.047	1.2	7.50	SPR	CG	Z
0.281	7.14	M-25	.56	14.3	.179	4.5	158	28	.10	2.4	15	67	.33	8.4	0.051	1.3	6.50	SST	CG	N
0.281	7.14	S-1181	.56	14.3	.177	4.5	169	30	.09	2.4	16	71	.34	8.6	0.052	1.3	6.50	SST	CG	N
0.281	7.14	S-1076	.56	14.3	.173	4.4	182	32	.10	2.5	18	79	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.281	7.14	J-57	.59	15.1	.233	5.9	6.6	1.2	.42	11	2.8	12	.17	4.4	0.024	0.6	6.25	MW	C	GI
0.281	7.14	10845	.59	15.1	.231	5.9	4.2	.74	.37	9.3	1.6	6.9	.23	5.7	0.025	0.6	9.00	SST	CG	N
0.281	7.14	S-1366	.59	15.1	.187	4.7	79	14	.16	4.1	13	57	.38	9.6	0.047	1.2	8.00	SST	CG	N
0.281	7.14	S-1044	.59	15.1	.185	4.7	89	16	.15	3.9	14	60	.38	9.8	0.048	1.2	8.00	SST	CG	N
0.281	7.14	11836	.59	15.1	.185	4.7	89	16	.15	3.9	14	60	.38	9.8	0.048	1.2	8.00	SST	CG	N
0.281	7.14	B9-4	.63	15.9	.237	6.0	8.6	1.5	.26	6.7	2.3	10	.12	2.9	0.022	0.6	4.25	MW	C	BO
0.281	7.14	A9-28	.63	15.9	.219	5.6	15	2.7	.36	9.2	5.6	25	.26	6.7	0.031	0.8	7.50	MW	C	GI
0.281	7.14	GG-33	.63	15.9	.205	5.2	29	5.0	.24	6.1	6.9	31	.32	8.2	0.038	1.0	8.50	SST	CG	N
0.281	7.14	3888	.63	15.9	.201	5.1	44	7.7	.19	4.9	8.5	38	.32	8.1	0.040	1.0	8.00	SPR	CG	Z
0.281	7.14	Y-32	.63	15.9	.195	5.0	54	9.4	.18	4.6	9.9	44	.34	8.7	0.043	1.1	8.00	SST	CG	N
0.281	7.14	B-76	.66	16.7	.223	5.7	10	1.8	.32	8.0	3.2	14	.25	6.3	0.029	0.7	7.50	SST	C	N
0.281	7.14	A9-53	.66	16.7	.219	5.6	13	2.2	.31	8.0	3.9	18	.25	6.3	0.031	0.8	8.00	SST	CG	N
0.281	7.14	BB-18	.69	17.4	.257	6.5	.10	.02	.48	12	.05	.20	.20	5.2	0.012	0.3	16.0	SST	C	N
0.281	7.14	12652	.69	17.4	.247	6.3	1.3	.23	.55	14	.72	3.2	.14	3.5	0.017	0.4	7.00	MW	C	Z
0.281	7.14	3543	.69	17.4	.233	5.9	8.0	1.4	.37	9.3	2.9	13	.16	4.0	0.024	0.6	5.50	MW	C	Z
0.281	7.14	B9-42	.69	17.4	.233	5.9	2.3	.41	.35	8.9	.82	3.7	.34	8.5	0.024	0.6	14.0	MW	CG	N
0.281	7.14	JJ-77	.69	17.4	.231	5.9	8.4	1.5	.37	9.5	3.1	14	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.281	7.14	10885	.69	17.4	.221	5.6	11	2.0	.40	10	4.6	20	.29	7.2	0.030	0.8	8.50	MW	C	GI
0.281	7.14	S-1252	.69	17.4	.219	5.6	15	2.6	.27	6.8	3.9	18	.22	5.5	0.031	0.8	7.00	SST	CG	N
0.281	7.14	3592	.69	17.4	.217	5.5	18	3.1	.36	9.3	6.5	29	.27	6.9	0.032	0.8	7.50	MW	C	Z
0.281	7.14	DD-91	.69	17.4	.215	5.5	14	2.4	.34	8.7	4.7	21	.33	8.4	0.033	0.8	9.00	SST	C	N
0.281	7.14	HH-17	.69	17.4	.205	5.2	34	5.9	.20	5.2	6.9	31	.29	7.2	0.038	1.0	7.50	SST	CG	N
0.281	7.14	XX-12	.69	17.4	.187	4.7	100	17	.14	3.5	14	60	.35	9.0	0.047	1.2	7.50	SPR	CG	Z
0.281	7.14	AA-32	.69	17.4	.181	4.6	104	18	.15	3.7	15	67	.45	11.4	0.050	1.3	9.00	SPR	CG	N
0.281	7.14	A-100	.72	18.2	.233	5.9	4.3	.76	.49	12	2.1	9.4	.23	5.8	0.024	0.6	8.50	MW	C	Z
0.281	7.14	10170	.72	18.2	.231	5.9	5.1	.90	.48	12	2.5	11	.24	6.0	0.025	0.6	8.50	MW	C	N
0.281	7.14	DD-41	.72	18.2	.201	5.1	67	12	.12	3.0	8.0	36	.26	6.6	0.040	1.0	5.50	SST	C	N
0.281	7.14	DD-53	.75	19.1	.249	6.3	1.1	.19	.53	14	.59	2.6	.11	2.8	0.016	0.4	6.00	SST	C	N
0.281	7.14	4294	.75	19.1	.231	5.9	5.1	.90	.51	13	2.6	12	.24	6.0	0.025	0.6	8.50	MW	C	N
0.281	7.14	3710	.75	19.1	.225	5.7	9.1	1.6	.48	12	4.4	19	.22	5.7	0.028	0.7	8.00	MW	CG	GI
0.281	7.14	S-927	.75	19.1	.225	5.7	10	1.8	.29	7.3	2.9	13	.22	5.5	0.028	0.7	6.75	SST	C	N
0.281	7.14	M-130	.75	19.1	.219	5.6	9.2	1.6	.41	10	3.8	17	.34	8.7	0.031	0.8	10.0	SST	C	N
0.281	7.14	G-20	.75	19.1	.217	5.5	9.8	1.7	.37	9.3	3.6	16	.38	9.8	0.032	0.8	12.0	HD	CG	N
0.281	7.14	B-91	.75	19.1	.217	5.5	12	2.1	.38	9.7	4.7	21	.35	8.9	0.032	0.8	10.0	HD	C	N
0.281	7.14	G-67	.75	19.1	.201	5.1	31	5.4	.26	6.5	8.0	36	.38	9.7	0.040	1.0	9.50	SST	CG	N
0.281	7.14	VV-68	.75	19.1	.199	5.1	37	6.4	.24	6.0	8.6	38	.41	10.4	0.041	1.0	9.00	SST	C	N
0.281	7.14	S-914	.78	19.8	.249	6.3	1.1	.20	.52	13	.59	2.6	.11	2.8	0.016	0.4	6.00	SST	C	N
0.281	7.14	I-97	.78	19.8	.245	6.2	1.2	.21	.62	16	.76	3.4	.16	4.1	0.018	0.5	8.00	SST	C	N
0.281	7.14	HH-49	.78	19.8	.229	5.8	6.0	1.0	.39	10	2.4	10	.23	5.8	0.026	0.7	7.75	SST	C	N
0.281	7.14	JJ-65	.78	19.8	.201	5.1	29	5.1	.29	7.4	8.5	38	.44	11.2	0.040	1.0	11.0	SPR	CG	Z
0.281	7.14	W-94	.81	20.6	.253	6.4	.42	.07	.69	17	.29	1.3	.13	3.2	0.014	0.4	8.00	SST	C	N
0.281	7.14	S-363	.81	20.6	.251	6.4	.19	.03	.50	13	.09	.41	.32	8.0	0.015	0.4	20.0	SST	C	N
0.281	7.14	O-64	.81	20.6	.219	5.6	10.6	1.9	.375	9.53	4.0	18.1	.280	7.08	0.031	0.8	9.00	SST	CG	N
0.281	7.14	3703	.84	21.4	.191	4.9	56	9.8	.21	5.4	12	53	.45	11.4	0.045	1.1	10.0	SPR	CG	Z
0.281	7.14	3609	.88	22.2	.249	6.3	.46	.08	.65	17	.30	1.3	.22	5.7	0.016	0.4	13.0	MW	C	Z
0.281	7.14	EE-28	.88	22.2	.241	6.1	2.0	.35	.69	17	1.4	6.1	.19	4.8	0.020	0.5	8.50	MW	C	N
0.281	7.14	S-1190	.88	22.2	.223	5.7	12	2.0	.28	7.1	3.2	14	.22	5.7	0.029	0.7	6.75	SST	C	N
0.281	7.14	A10-19	.88	22.2	.213	5.4	15	2.7	.50	13	7.7	34	.35	8.9	0.034	0.9	10.3	MW	CG	N
0.281	7.14	OO-64	.88	22.2	.211	5.4	18	3.2	.32	8.1	5.8	26	.35	8.9	0.035	0.9	10.0	SPR	CG	N
0.281	7.14	Q-88	.88	22.2	.209	5.3	21	3.6	.31	7.8	6.3	28	.40	10.1	0.036	0.9	10.0	SPR	C	GI
0.281	7.14	AA-17	.88	22.2	.181	4.6	79	14	.18	4.6	14	63	.50	12.7	0.050	1.3	10.0	SST	CG	N
0.281	7.14	3531	.91	23.0	.201	5.1	29	5.1	.40	10	12	53	.44	11.2	0.040	1.0	11.0	MW	CG	GI
0.281	7.14	U-14	.91	23.0	.199	5.1	37	6.4	.25	6.3	9.2	41	.41	10.4	0.041	1.0	10.0	SPR	CG	GI
0.281	7.14	G-53	.94	23.8	.245	6.2	1.3	.22	.77	19	.98	4.4	.17	4.3	0.018	0.5	8.50	MW	C	N
0.281	7.14	HH-28	.94	23.8	.245	6.2	1.1	.19	.75	19	.83	3.7	.19	4.8	0.018	0.5	9.50	MW	C	BO
0.281	7.14	CC-28	.94	23.8	.241	6.1	1.4	.25	.70	18	1.0	4.5	.24	6.1	0.020	0.5	11.0	MW	C	Z
0.281	7.14	S-107	.94	23.8	.225	5.7	5.8	1.0	.51	13	2.9	13	.32	8.0	0.028	0.7	10.3	SST	C	N
0.281	7.14	10827	1.00	25.4	.251	6.4	.62	.11	.78	20	.48	2.2	.11	2.9	0.015	0.4	7.50	SST	CG	N
0.281	7.14	2632	1.00	25.4	.251	6.4	.32	.06	.78	20</										




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.281	7.14	S-998	1.00	25.4	.181	4.6	63	11	.23	5.7	14	63	.60	15.2	0.050	1.3	12.0	SST	CG	N
0.281	7.14	BB-51	1.00	25.4	.181	4.6	81	14	.19	4.8	15	67	.55	14.0	0.050	1.3	11.0	SPR	CG	N
0.281	7.14	S-1053	1.00	25.4	.177	4.5	90	16	.18	4.5	16	71	.55	13.9	0.052	1.3	10.5	SST	CG	N
0.281	7.14	934	1.00	25.4	.173	4.4	149	26	.13	3.2	19	84	.54	13.7	0.054	1.4	9.00	HD	C	Z
0.281	7.14	BB-90	1.00	25.4	.173	4.4	104	18	.18	4.6	19	84	.65	16.5	0.054	1.4	12.0	SPR	CG	Z
0.281	7.14	KK-88	1.00	25.4	.157	4.0	202	35	.14	3.5	28	124	.74	18.9	0.062	1.6	12.0	SPR	CG	N
0.281	7.14	10983	1.03	26.2	.219	5.6	8.4	1.5	.47	12	3.9	18	.34	8.7	0.031	0.8	11.0	SST	CG	N
0.281	7.14	11352	1.03	26.2	.211	5.4	9.3	1.6	.44	11	4.2	18	.59	14.9	0.035	0.9	15.8	SST	C	N
0.281	7.14	H-13	1.06	27.0	.237	6.0	1.2	.22	.71	18	.87	3.9	.35	8.9	0.022	0.6	16.0	SST	CG	N
0.281	7.14	Q-92	1.06	27.0	.201	5.1	22	3.8	.39	9.9	8.5	38	.56	14.2	0.040	1.0	14.0	SPR	CG	Z
0.281	7.14	2630	1.09	27.8	.245	6.2	.92	.16	.88	22	.81	3.6	.22	5.5	0.018	0.5	11.0	MW	C	Z
0.281	7.14	L-7	1.09	27.8	.229	5.8	4.4	.77	.78	20	3.4	15	.31	7.9	0.026	0.7	11.0	MW	C	N
0.281	7.14	H-59	1.09	27.8	.211	5.4	11	2.0	.52	13	5.8	26	.53	13.3	0.035	0.9	15.0	SPR	CG	N
0.281	7.14	HH-99	1.13	28.6	.243	6.2	.82	.14	.86	22	.71	3.1	.27	6.8	0.019	0.5	13.0	SST	C	N
0.281	7.14	3995	1.13	28.6	.225	5.7	4.8	.85	.73	18	3.5	16	.40	10.1	0.028	0.7	13.3	MW	C	Z
0.281	7.14	EE-57	1.13	28.6	.221	5.6	6.7	1.2	.71	18	4.7	21	.42	10.7	0.030	0.8	13.0	MW	C	N
0.281	7.14	3510	1.13	28.6	.215	5.5	10	1.8	.66	17	6.7	30	.46	11.7	0.033	0.8	13.0	MW	C	Z
0.281	7.14	2839	1.13	28.6	.213	5.4	9.3	1.6	.56	14	5.2	23	.57	14.5	0.034	0.9	15.8	MW	C	Z
0.281	7.14	3767	1.13	28.6	.211	5.4	13	2.3	.44	11	5.8	26	.46	11.6	0.035	0.9	13.0	SPR	C	Z
0.281	7.14	3450	1.19	30.2	.233	5.9	2.6	.45	.85	22	2.2	9.7	.34	8.5	0.024	0.6	13.0	MW	C	Z
0.281	7.14	A13-52	1.19	30.2	.209	5.3	8.4	1.5	.49	13	4.2	19	.69	17.6	0.036	0.9	19.3	SST	CG	N
0.281	7.14	1729	1.25	31.8	.265	6.7	.04	.01	1.2	30	.04	.19	.09	2.2	0.008	0.2	10.0	MW	C	TI
0.281	7.14	DD-20	1.25	31.8	.245	6.2	1.0	.18	1.1	27	1.1	4.9	.20	5.0	0.018	0.5	10.0	MW	C	N
0.281	7.14	O-83	1.25	31.8	.243	6.2	.80	.14	.95	24	.76	3.4	.30	7.7	0.019	0.5	15.0	MW	C	N
0.281	7.14	410	1.25	31.8	.231	5.9	2.0	.34	.95	24	1.8	8	.31	7.8	0.025	0.6	11.3	B	C	BO
0.281	7.14	3806	1.25	31.8	.225	5.7	5.2	.91	.84	21	4.4	19	.38	9.6	0.028	0.7	12.5	MW	C	GI
0.281	7.14	I-65	1.25	31.8	.225	5.7	4.7	.83	.84	21	4.0	18	.41	10.3	0.028	0.7	13.5	MW	C	Z
0.281	7.14	4212	1.25	31.8	.219	5.6	7.1	1.2	.79	20	5.6	25	.47	11.8	0.031	0.8	14.0	MW	C	Z
0.281	7.14	A11-56	1.25	31.8	.215	5.5	9.3	1.6	.55	14	5.1	23	.46	11.7	0.033	0.8	14.0	SPR	CG	N
0.281	7.14	3585	1.25	31.8	.195	5.0	36	6.4	.29	7.3	11	47	.52	13.1	0.043	1.1	12.0	SPR	CG	Z
0.281	7.14	NN-99	1.25	31.8	.181	4.6	56	9.8	.27	6.9	15	67	.75	19.1	0.050	1.3	15.0	SPR	CG	Z
0.281	7.14	B10-46	1.28	32.5	.211	5.4	16	2.8	.36	9.1	5.8	26	.39	9.8	0.035	0.9	11.0	SPR	CG	N
0.281	7.14	1637	1.28	32.5	.165	4.2	173	30	.13	3.4	23	103	.61	15.5	0.058	1.5	10.5	SPR	CG	Z
0.281	7.14	1927	1.31	33.3	.237	6.0	2.4	.42	.94	24	2.3	10	.24	6.1	0.022	0.6	10.0	MW	C	GI
0.281	7.14	B11-49	1.31	33.3	.199	5.1	33	5.7	.28	7.1	9.2	41	.45	11.5	0.041	1.0	11.0	SPR	CG	Z
0.281	7.14	NN-65	1.34	34.1	.229	5.8	3.6	.63	.98	25	3.5	16	.36	9.2	0.026	0.7	13.0	MW	C	N
0.281	7.14	10911	1.34	34.1	.191	4.9	33	5.8	.36	9.2	12	53	.74	18.9	0.045	1.1	15.5	SPR	C	N
0.281	7.14	W-4	1.34	34.1	.161	4.1	125	22	.19	4.8	24	106	.84	21.3	0.060	1.5	14.0	SST	CG	N
0.281	7.14	00-92	1.38	34.9	.251	6.4	.39	.07	1.2	30	.46	2.0	.20	5.0	0.015	0.4	12.0	MW	C	N
0.281	7.14	4	1.38	34.9	.225	5.7	4.4	.76	.94	24	4.1	18	.43	11.0	0.028	0.7	14.5	MW	C	Z
0.281	7.14	3772	1.38	34.9	.221	5.6	4.1	.72	.75	19	3.0	14	.63	16.0	0.030	0.8	20.0	MW	C	Z
0.281	7.14	AA-9	1.38	34.9	.221	5.6	8.2	1.4	.65	17	5.4	24	.33	8.4	0.030	0.8	11.0	MW	CG	Z
0.281	7.14	3630	1.38	34.9	.181	4.6	43	7.5	.43	11	18	81	.95	24.1	0.050	1.3	19.0	MW	CG	Z
0.281	7.14	HH-9	1.38	34.9	.181	4.6	73	13	.21	5.3	15	67	.60	15.2	0.050	1.3	12.0	SPR	CG	N
0.281	7.14	2964	1.41	35.7	.219	5.6	6.1	1.1	.88	22	5.3	24	.53	13.4	0.031	0.8	16.0	MW	C	Z
0.281	7.14	2655	1.41	35.7	.215	5.5	10	1.8	.70	18	7.1	31	.46	11.7	0.033	0.8	13.0	MW	C	Z
0.281	7.14	LL-47	1.44	36.5	.221	5.6	7.0	1.2	.76	19	5.4	24	.41	10.3	0.030	0.8	12.5	MW	C	Z
0.281	7.14	S-1075	1.50	38.1	.217	5.5	5.3	.93	.82	21	4.3	19	.58	14.6	0.032	0.8	18.0	SST	CG	N
0.281	7.14	NN-72	1.50	38.1	.201	5.1	10	1.8	.50	13	5.1	23	1.00	25.4	0.040	1.0	25.0	SST	CG	N
0.281	7.14	JJ-85	1.50	38.1	.171	4.3	95	17	.21	5.3	20	88	.77	19.6	0.055	1.4	14.0	SPR	CG	Z
0.281	7.14	HH-41	1.56	39.7	.181	4.6	33	5.8	.43	11	14	63	1.08	27.3	0.050	1.3	21.5	SST	CG	N
0.281	7.14	L-60-A	1.63	41.3	.231	5.9	2.0	.36	1.1	29	2.3	10	.49	12.4	0.025	0.6	18.5	MW	C	N
0.281	7.14	S-1145	1.63	41.3	.231	5.9	.83	.15	.68	17	.56	2.5	.95	24.1	0.025	0.6	37.0	SST	C	N
0.281	7.14	2795	1.63	41.3	.223	5.7	4.0	.70	1.1	27	4.3	19	.55	14.0	0.029	0.7	18.0	MW	C	Z
0.281	7.14	HH-59	1.63	41.3	.221	5.6	5.3	.92	1.0	26	5.4	24	.48	12.2	0.030	0.8	16.0	MW	CG	GI
0.281	7.14	BB-91	1.63	41.3	.211	5.4	7.0	1.2	.77	20	5.4	24	.70	17.8	0.035	0.9	20.0	SST	CG	N
0.281	7.14	10433	1.63	41.3	.199	5.1	17	3.0	.54	14	9.2	41	.79	20.0	0.041	1.0	19.3	SPR	CG	N
0.281	7.14	UU-67	1.75	44.5	.243	6.2	.65	.11	1.4	36	.92	4.1	.32	8.2	0.019	0.5	16.0	SST	C	N
0.281	7.14	S-1338	1.75	44.5	.241	6.1	.75	.13	1.4	35	1.0	4.6	.36	9.1	0.020	0.5	17.0	SST	C	N
0.281	7.14	3622	1.84	46.8	.153	3.9	157	28	.27	6.8	42	187	1.15	29.3	0.064	1.6	17.0	MW	C	Z
0.281	7.14	K-33	2.00	50.8	.233	5.9	1.8	.32	1.6	40	2.8	13	.44	11.3	0.024	0.6	17.5	MW	C	Z
0.281	7.14	L-38	2.00	50.8	.225	5.7	2.6	.45	1.3	34	3.5	15	.67	17.1	0.028	0.7	23.0	MW	C	Z
0.281	7.14	S-1368	2.00	50.8	.215	5.5	3.8	.66	1.1	28	4.1	18	.92	23.3	0.033	0.8	27.8	SST	CG	N
0.281	7.14	NN-12	2.03	51.6	.201	5.1	8.6	1.5	.87	22	7.5	33	1.16	29.5	0.040	1.0	29.0	SST	CG	N
0.281	7.14	12331	2.06	52.4	.225	5.7	2.6	.45	1.4	35	3.6	16	.67	17.1	0.028	0.7	23.0	MW	C	Z
0.281	7.14	B10-35	2.44	61.9	.223	5.7	3.7	.64	1.3	33	4.8	22	.59	14.9	0.029	0.7	19.3	MW	C	Z
0.281	7.14	10812	2.50	63.5	.243	6.2	.31	.05	1.9	48	.58	2.6	.61	15.4	0.019	0.5	32.0	SST	CG	N
0.281	7.14	B11-65	2.53	64.3	.183	4.6	30	5.3	.51	13	15	68	1.23	31.1	0.049	1.2	24.0	SPR	C	Z
0																				




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	GG-22	.25	6.4	.224	5.7	91	16	.07	1.7	6.0	27	.16	4.1	0.036	0.9	3.50	SPR	C	N
0.296	7.52	HH-19	.25	6.4	.216	5.5	130	23	.06	1.5	7.6	34	.14	3.6	0.040	1.0	3.50	SST	CG	N
0.296	7.52	Q-16	.28	7.1	.258	6.6	2.9	.51	.19	4.7	.54	2.4	.10	2.4	0.019	0.5	5.00	MW	CG	N
0.296	7.52	B-19	.28	7.1	.214	5.4	107	19	.08	1.9	8.2	36	.16	4.2	0.041	1.0	4.00	SST	CG	N
0.296	7.52	W-88	.28	7.1	.202	5.1	195	34	.06	1.6	12	54	.19	4.8	0.047	1.2	4.00	SST	CG	N
0.296	7.52	M-11	.30	7.5	.226	5.7	42	7.3	.12	3.1	5.2	23	.16	4.0	0.035	0.9	4.50	SST	CG	N
0.296	7.52	12647	.30	7.5	.236	6.0	18	3.1	.15	3.7	2.6	12	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.296	7.52	B3-48	.30	7.5	.214	5.4	122	21	.09	2.3	11	50	.21	5.2	0.041	1.0	4.00	MW	C	GI
0.296	7.52	B-9	.31	7.9	.248	6.3	10	1.8	.18	4.6	1.9	8.3	.12	3.0	0.024	0.6	4.00	SST	C	N
0.296	7.52	IL-100	.31	7.9	.214	5.4	107	19	.08	1.9	8.2	36	.16	4.2	0.041	1.0	4.00	SST	CG	N
0.296	7.52	XX-6	.31	7.9	.176	4.5	933	163	.03	.66	24	108	.21	5.3	0.060	1.5	3.50	SPR	CG	N
0.296	7.52	O-127	.31	7.9	.172	4.4	818	143	.03	.83	27	119	.25	6.3	0.062	1.6	4.00	SPR	CG	N
0.296	7.52	F-47	.34	8.7	.266	6.8	.93	.16	.25	6.2	.23	1.0	.10	2.5	0.015	0.4	5.50	MW	C	Z
0.296	7.52	W-10	.34	8.7	.244	6.2	9.6	1.7	.19	4.7	1.8	8.0	.16	4.0	0.026	0.7	5.00	SST	C	N
0.296	7.52	EE-75	.34	8.7	.236	6.0	20	3.6	.16	4.1	3.3	15	.18	4.6	0.030	0.8	5.00	MW	C	Z
0.296	7.52	W-32	.34	8.7	.214	5.4	86	15	.10	2.4	8.2	36	.23	5.7	0.041	1.0	4.50	SST	C	N
0.296	7.52	Q-78	.34	8.7	.196	5.0	238	42	.06	1.5	14	64	.23	5.7	0.050	1.3	4.50	SPR	CG	N
0.296	7.52	B18-131	.38	9.5	.278	7.1	.03	.01	.23	5.9	.01	.03	.14	3.7	0.009	0.2	15.0	MW	C	Z
0.296	7.52	NN-1	.38	9.5	.266	6.8	.54	.09	.24	6.1	.13	.58	.14	3.4	0.015	0.4	8.00	MW	C	N
0.296	7.52	WW-34	.38	9.5	.266	6.8	.46	.08	.23	5.7	.10	.46	.15	3.8	0.015	0.4	9.00	MW	C	Z
0.296	7.52	V-15	.38	9.5	.256	6.5	1.2	.21	.18	4.4	.21	.92	.20	5.1	0.020	0.5	10.0	SST	CG	N
0.296	7.52	JJ-59	.38	9.5	.254	6.5	2.9	.51	.23	5.8	.66	2.9	.15	3.7	0.021	0.5	6.00	SST	C	N
0.296	7.52	G-77	.38	9.5	.248	6.3	5.1	.89	.21	5.3	1.1	4.7	.17	4.3	0.024	0.6	6.00	SST	C	N
0.296	7.52	B8-5	.38	9.5	.230	5.8	27	4.7	.18	4.6	4.9	22	.18	4.6	0.033	0.8	5.50	SPR	CG	N
0.296	7.52	M-55	.38	9.5	.222	5.6	68	12	.10	2.4	6.5	29	.16	4.0	0.037	0.9	4.25	SPR	CG	N
0.296	7.52	B12-41	.38	9.5	.220	5.6	78	14	.09	2.3	7.0	31	.16	4.1	0.038	1.0	4.25	SPR	CG	N
0.296	7.52	K-72	.38	9.5	.202	5.1	130	23	.09	2.4	12	54	.24	6.0	0.047	1.2	5.00	SST	CG	N
0.296	7.52	2966	.38	9.5	.196	5.0	199	35	.07	1.9	14	64	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.296	7.52	A10-22	.41	10.3	.256	6.5	2.2	.38	.27	6.8	.58	2.6	.14	3.6	0.020	0.5	7.00	MW	CG	N
0.296	7.52	11137	.41	10.3	.240	6.1	5.7	1.0	.10	2.5	.56	2.5	.31	7.8	0.028	0.7	10.0	MW	C	N
0.296	7.52	A15-34	.41	10.3	.230	5.8	31	5.4	.22	5.5	6.7	30	.17	4.2	0.033	0.8	5.00	MW	CG	N
0.296	7.52	A11-39	.41	10.3	.218	5.5	69	12	.10	2.6	7.1	31	.18	4.5	0.039	1.0	4.50	SST	CG	N
0.296	7.52	A15-31	.41	10.3	.212	5.4	96	17	.09	2.3	8.8	39	.19	4.8	0.042	1.1	4.50	SST	CG	N
0.296	7.52	L-5	.41	10.3	.202	5.1	120	21	.11	2.8	13	58	.27	6.9	0.047	1.2	5.75	SPR	CG	N
0.296	7.52	B1-24	.44	11.1	.246	6.2	9.9	1.7	.20	5.1	2.0	8.9	.14	3.5	0.025	0.6	4.50	SST	C	N
0.296	7.52	A11-6	.44	11.1	.244	6.2	13	2.3	.25	6.4	3.3	15	.12	3.0	0.026	0.7	4.50	MW	CG	GI
0.296	7.52	A10-10	.44	11.1	.236	6.0	18	3.2	.19	4.8	3.4	15	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.296	7.52	Z-98	.44	11.1	.234	5.9	21	3.7	.18	4.5	3.8	17	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.296	7.52	IL-98	.44	11.1	.232	5.9	20	3.6	.20	5.1	4.1	18	.19	4.7	0.032	0.8	5.00	SST	C	N
0.296	7.52	B-70	.44	11.1	.226	5.7	40	7.0	.14	3.5	5.5	25	.18	4.4	0.035	0.9	5.00	SPR	CG	GI
0.296	7.52	JJ-98	.44	11.1	.210	5.3	75	13	.13	3.2	9.4	42	.24	6.0	0.043	1.1	5.50	SST	CG	N
0.296	7.52	A-13	.47	11.9	.274	7.0	.30	.05	.40	10	.12	.54	.07	1.7	0.011	0.3	5.00	MW	C	N
0.296	7.52	PP-13	.47	11.9	.264	6.7	.94	.17	.35	8.8	.33	1.5	.12	3.0	0.016	0.4	6.50	MW	C	N
0.296	7.52	L-73	.47	11.9	.254	6.5	4.4	.78	.34	8.7	1.5	6.7	.13	3.2	0.021	0.5	5.00	MW	C	Z
0.296	7.52	O-82	.47	11.9	.244	6.2	10	1.8	.21	5.4	2.2	10	.12	3.1	0.026	0.7	4.75	SST	CG	N
0.296	7.52	Z-16	.47	11.9	.238	6.0	13	2.3	.29	7.5	3.9	17	.17	4.4	0.029	0.7	6.00	MW	CG	N
0.296	7.52	A13-59	.47	11.9	.214	5.4	61	11	.13	3.4	8.2	36	.23	5.7	0.041	1.0	5.50	SST	CG	N
0.296	7.52	A11-10	.47	11.9	.210	5.3	67	12	.14	3.6	9.4	42	.26	6.6	0.043	1.1	6.00	SST	CG	N
0.296	7.52	LL-60	.50	12.7	.276	7.0	.20	.04	.44	11	.09	.40	.06	1.5	0.010	0.3	5.00	MW	C	Z
0.296	7.52	10834	.50	12.7	.272	6.9	.18	.03	.39	9.8	.07	.31	.11	2.9	0.012	0.3	8.50	SST	C	N
0.296	7.52	IL-84	.50	12.7	.272	6.9	.13	.02	.36	9.1	.05	.20	.14	3.6	0.012	0.3	10.8	SST	C	N
0.296	7.52	NN-58	.50	12.7	.272	6.9	.14	.03	.36	9.0	.05	.23	.14	3.7	0.012	0.3	11.0	MW	C	N
0.296	7.52	B15-35	.50	12.7	.272	6.9	.22	.04	.39	10	.09	.38	.11	2.7	0.012	0.3	8.00	MW	C	N
0.296	7.52	NN-62	.50	12.7	.264	6.7	.46	.08	.32	8.2	.15	.67	.18	4.5	0.016	0.4	10.0	SST	C	N
0.296	7.52	JJ-24	.50	12.7	.260	6.6	2.3	.41	.39	10	.91	4.0	.11	2.7	0.018	0.5	5.00	MW	C	N
0.296	7.52	XX-29	.50	12.7	.254	6.5	3.9	.67	.32	8.3	1.3	5.6	.13	3.2	0.021	0.5	5.00	SST	C	N
0.296	7.52	PP-70	.50	12.7	.252	6.4	5.4	.95	.37	9.3	2.0	8.8	.13	3.4	0.022	0.6	5.00	MW	C	Z
0.296	7.52	A15-9	.50	12.7	.250	6.4	7.8	1.4	.32	8.0	2.5	11	.10	2.6	0.023	0.6	4.50	MW	CG	N
0.296	7.52	AA-8	.50	12.7	.244	6.2	3.8	.67	.25	6.4	.97	4.3	.25	6.3	0.026	0.7	9.50	SST	CG	N
0.296	7.52	S-296	.50	12.7	.244	6.2	9.6	1.7	.23	5.9	2.2	10	.16	4.0	0.026	0.7	5.00	SST	C	N
0.296	7.52	B18-136	.50	12.7	.236	6.0	18	3.1	.29	7.3	5.1	23	.17	4.2	0.030	0.8	5.50	MW	CG	Z
0.296	7.52	K-1	.50	12.7	.234	5.9	14	2.5	.25	6.4	3.6	16	.25	6.3	0.031	0.8	7.00	MW	C	Z
0.296	7.52	I-71	.50	12.7	.232	5.9	27	4.8	.16	4.1	4.4	20	.16	4.1	0.032	0.8	5.00	SPR	CG	N
0.296	7.52	Z-43	.50	12.7	.230	5.8	19	3.2	.24	6.0	4.4	19	.26	6.7	0.033	0.8	7.00	SPR	C	Z
0.296	7.52	2563	.50	12.7	.218	5.5	65	11	.12	2.9	7.6	34	.23	5.9	0.039	1.0	5.00	SPR	C	Z
0.296	7.52	K-97	.50	12.7	.212	5.4	67	12	.13	3.3	8.8	39	.23	5.9	0.042	1.1	5.50	SST	CG	N
0.296	7.52	B15-59	.50	12.7	.208	5.3	84	15	.13	3.2	11	48	.26	6.7	0.044	1.1	6.00	SPR	CG	Z
0.296	7.52	M-22	.50	12.7	.204	5.2	118	21	.10	2.6	12	54	.25	6.4	0.046	1.2	5.50	SPR	CG	N
0.296	7.52	10962	.50	12.7	.194	4.9	147	26	.10	2.5	14	64	.31	7.8	0.051	1.3	6.00	SST	CG	Z
0.296	7.52	W-20	.50	12.7	.162	4.1	592	104	.05	1.3	31	138	.37	9.4	0.067	1.7				




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	S-1372	.56	14.3	.226	5.7	23	4.1	.22	5.7	5.2	23	.23	5.8	0.035	0.9	6.50	SST	CG	N
0.296	7.52	O-126	.56	14.3	.216	5.5	64	11	.12	3.0	7.6	34	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.296	7.52	J-65	.56	14.3	.202	5.1	112	20	.12	2.9	13	58	.33	8.4	0.047	1.2	6.00	SPR	C	Z
0.296	7.52	S-1696	.58	14.7	.234	5.9	16	2.7	.24	6.2	3.8	17	.22	5.5	0.031	0.8	6.00	SST	C	N
0.296	7.52	12404	.59	15.1	.268	6.8	.55	.10	.49	12	.27	1.2	.11	2.7	0.014	0.4	6.50	MW	C	N
0.296	7.52	B1-70	.59	15.1	.248	6.3	6.9	1.2	.27	6.8	1.9	8.3	.14	3.7	0.024	0.6	5.00	SST	C	N
0.296	7.52	M-103	.59	15.1	.246	6.2	5.4	.94	.37	9.4	2.0	8.9	.16	4.1	0.025	0.6	6.50	SST	CG	N
0.296	7.52	B8-17	.59	15.1	.228	5.8	21	3.7	.25	6.3	5.3	24	.24	6.0	0.034	0.9	7.00	SPR	CG	N
0.296	7.52	H-74	.59	15.1	.202	5.1	107	19	.11	2.9	12	54	.27	6.9	0.047	1.2	5.75	SST	CG	N
0.296	7.52	4283	.63	15.9	.270	6.9	.33	.06	.51	13	.17	.75	.11	2.8	0.013	0.3	7.50	MW	C	N
0.296	7.52	10854	.63	15.9	.262	6.7	1.2	.21	.51	13	.62	2.8	.12	3.0	0.017	0.4	6.00	SST	C	N
0.296	7.52	B12-36	.63	15.9	.252	6.4	5.5	.96	.40	10	2.2	9.6	.11	2.8	0.022	0.6	5.00	MW	CG	N
0.296	7.52	3193	.63	15.9	.246	6.2	8.0	1.4	.37	9.5	3.0	13	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.296	7.52	11-24	.63	15.9	.246	6.2	4.9	.85	.41	10	2.0	8.9	.20	5.1	0.025	0.6	7.00	SST	C	N
0.296	7.52	B3-60	.63	15.9	.246	6.2	4.3	.76	.41	10	1.8	8.0	.21	5.4	0.025	0.6	8.50	MW	CG	Z
0.296	7.52	AA-98	.63	15.9	.240	6.1	7.2	1.3	.39	9.9	2.8	12	.21	5.3	0.028	0.7	7.50	SST	CG	N
0.296	7.52	L-81	.63	15.9	.232	5.9	18	3.2	.25	6.3	4.4	20	.24	6.1	0.032	0.8	6.50	HD	C	N
0.296	7.52	10077	.63	15.9	.228	5.8	21	3.7	.25	6.4	5.3	24	.27	6.9	0.034	0.9	7.00	SPR	CG	Z
0.296	7.52	A12-39	.63	15.9	.216	5.5	58	10	.19	4.9	11	50	.23	5.8	0.040	1.0	5.75	MW	CG	GI
0.296	7.52	A11-19	.63	15.9	.204	5.2	66	11	.17	4.4	11	51	.35	8.8	0.046	1.2	7.50	SST	CG	N
0.296	7.52	F-65	.63	15.9	.202	5.1	90	16	.14	3.7	13	58	.38	9.6	0.047	1.2	7.00	HD	C	Z
0.296	7.52	BB-19	.63	15.9	.196	5.0	89	16	.15	3.9	14	61	.40	10.2	0.050	1.3	8.00	SST	CG	N
0.296	7.52	3861	.63	15.9	.192	4.9	102	18	.16	4.0	16	71	.47	11.9	0.052	1.3	9.00	SPR	CG	Z
0.296	7.52	I-16	.63	15.9	.188	4.8	148	26	.11	2.9	17	76	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.296	7.52	NN-61	.66	16.7	.256	6.5	2.2	.38	.50	13	1.1	4.8	.16	4.1	0.020	0.5	7.00	MW	C	N
0.296	7.52	S-1015	.66	16.7	.240	6.1	9.9	1.7	.28	7.2	2.8	12	.17	4.3	0.028	0.7	6.00	SST	CG	N
0.296	7.52	00-6	.66	16.7	.236	6.0	14	2.4	.37	9.4	5.1	23	.20	5.0	0.030	0.8	6.50	MW	CG	Z
0.296	7.52	EE-91	.66	16.7	.224	5.7	30	5.3	.20	5.0	6.0	27	.27	6.9	0.036	0.9	6.50	SPR	C	N
0.296	7.52	H-26	.66	16.7	.216	5.5	31	5.5	.24	6.2	7.6	34	.32	8.1	0.040	1.0	8.00	SST	CG	N
0.296	7.52	JJ-32	.66	16.7	.192	4.9	104	18	.15	3.7	15	68	.42	10.6	0.052	1.3	8.00	SST	CG	N
0.296	7.52	B9-1	.69	17.4	.254	6.5	3.8	.67	.49	12	1.9	8.4	.12	2.9	0.021	0.5	5.50	MW	CG	Z
0.296	7.52	11-34	.69	17.4	.246	6.2	4.1	.72	.46	12	1.9	8.5	.23	5.7	0.025	0.6	8.00	SST	C	N
0.296	7.52	MM-14	.69	17.4	.238	6.0	9.6	1.7	.47	12	4.5	20	.22	5.5	0.029	0.7	7.50	MW	CG	GI
0.296	7.52	11-47	.69	17.4	.236	6.0	12	2.2	.41	10	5.1	23	.24	6.1	0.030	0.8	7.00	MW	C	N
0.296	7.52	MM-29	.69	17.4	.236	6.0	11.2	1.9	.46	12	3.8	17	.23	5.7	0.030	0.8	7.50	MW	CG	Z
0.296	7.52	RR-9	.69	17.4	.222	5.6	21	3.6	.30	7.5	6.1	27	.35	8.9	0.037	0.9	8.50	SST	C	N
0.296	7.52	A14-1	.69	17.4	.212	5.4	45	7.9	.21	5.3	9.4	42	.34	8.5	0.042	1.1	8.00	SPR	CG	GI
0.296	7.52	F-42	.69	17.4	.204	5.2	74	13	.16	4.2	12	54	.39	9.9	0.046	1.2	7.50	SPR	C	Z
0.296	7.52	F-43	.69	17.4	.202	5.1	83	14	.16	4.0	13	58	.40	10.1	0.047	1.2	7.50	HD	C	Z
0.296	7.52	NN-19	.69	17.4	.196	5.0	67	12	.19	4.7	13	56	.50	12.7	0.050	1.3	10.0	SST	CG	N
0.296	7.52	A10-16	.72	18.2	.264	6.7	.68	.12	.58	15	.40	1.8	.14	3.5	0.016	0.4	7.50	SST	C	N
0.296	7.52	B1-16	.72	18.2	.252	6.4	3.6	.63	.40	10	1.4	6.4	.13	3.4	0.022	0.6	6.00	SST	CG	N
0.296	7.52	J-88	.72	18.2	.238	6.0	8.8	1.5	.49	12	4.3	19	.23	5.9	0.029	0.7	8.00	MW	CG	Z
0.296	7.52	4396	.72	18.2	.180	4.6	238	42	.09	2.4	22	98	.41	10.3	0.058	1.5	7.00	SPR	CG	Z
0.296	7.52	S-3010	.75	19.1	.268	6.8	.34	.06	.62	16	.21	.94	.13	3.3	0.014	0.4	8.25	SST	C	N
0.296	7.52	3172	.75	19.1	.266	6.8	.52	.09	.61	16	.32	1.4	.14	3.5	0.015	0.4	8.25	MW	C	Z
0.296	7.52	KK-16	.75	19.1	.256	6.5	.84	.15	.45	11	.38	1.7	.30	7.6	0.020	0.5	15.0	MW	CG	N
0.296	7.52	KK-3	.75	19.1	.256	6.5	1.2	.21	.51	13	.61	2.7	.24	6.1	0.020	0.5	11.0	MW	C	N
0.296	7.52	W-75	.75	19.1	.252	6.4	2.5	.44	.54	14	1.3	6.0	.21	5.3	0.022	0.6	8.50	MW	C	N
0.296	7.52	G-25	.75	19.1	.252	6.4	4.1	.72	.53	13	2.2	9.6	.15	3.9	0.022	0.6	6.00	MW	C	N
0.296	7.52	10727	.75	19.1	.244	6.2	5.3	.94	.51	13	2.7	12	.24	6.1	0.026	0.7	8.25	MW	C	N
0.296	7.52	MM-22	.75	19.1	.236	6.0	6.9	1.2	.45	11	3.1	14	.30	7.6	0.030	0.8	10.0	SST	CG	N
0.296	7.52	S-124	.75	19.1	.236	6.0	8.9	1.6	.39	9.8	3.4	15	.27	6.9	0.030	0.8	8.00	SST	C	N
0.296	7.52	3892	.75	19.1	.224	5.7	24	4.2	.25	6.3	6.0	27	.28	7.1	0.036	0.9	7.00	SPR	C	Z
0.296	7.52	O-76	.75	19.1	.216	5.5	37	6.4	.22	5.7	8.1	36	.32	8.1	0.040	1.0	8.00	SPR	CG	N
0.296	7.52	00-33	.75	19.1	.216	5.5	44	7.7	.19	4.7	8.1	36	.32	8.1	0.040	1.0	7.00	SPR	C	Z
0.296	7.52	I-45	.75	19.1	.206	5.2	55	9.6	.21	5.3	11	51	.39	10.0	0.045	1.1	8.75	SPR	CG	N
0.296	7.52	Q-86	.75	19.1	.202	5.1	75	13	.17	4.4	13	58	.38	9.6	0.047	1.2	8.00	SPR	CG	GI
0.296	7.52	J-6	.75	19.1	.202	5.1	64	11	.20	5.1	13	58	.47	11.9	0.047	1.2	9.00	SPR	C	Z
0.296	7.52	HH-21	.78	19.8	.256	6.5	2.7	.47	.60	15	1.6	7.2	.14	3.6	0.020	0.5	6.00	MW	C	N
0.296	7.52	O-157	.78	19.8	.246	6.2	5.4	.94	.37	9.4	2.0	8.9	.19	4.8	0.025	0.6	6.50	SST	C	N
0.296	7.52	10432	.78	19.8	.200	5.1	80	14	.17	4.4	14	61	.40	10.1	0.048	1.2	8.25	SPR	CG	BO
0.296	7.52	3523	.78	19.8	.176	4.5	155	27	.12	3.1	19	84	.66	16.8	0.060	1.5	11.0	SPR	CG	GI
0.296	7.52	L-57	.81	20.6	.260	6.6	.99	.17	.63	16	.63	2.8	.18	4.6	0.018	0.5	9.00	HD	C	Z
0.296	7.52	10869	.81	20.6	.256	6.5	1.9	.34	.56	14	1.1	4.8	.16	4.1	0.020	0.5	7.00	SST	C	N
0.296	7.52	A-19	.81	20.6	.256	6.5	1.2	.21	.59	15	.70	3.1	.22	5.6	0.020	0.5	10.0	SST	C	N
0.296	7.52	10221	.81	20.6	.246	6.2	5.6	.99	.53	13	3.0	13	.18	4.4	0.025	0.6	7.00	MW	CG	Z
0.296	7.52	A-96	.81	20.6	.232	5.9	12	2.0	.38	9.7	4.4	20	.29	7.3	0.032	0.8	9.00	SPR	CG	BO
0.296	7.52	B5-18	.81	20.6	.232	5.9	12	2.0	.38	9.6	4.4	20	.29	7.3	0.032	0.8	9.00	SPR	CG	N
0.																				





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	A14-49	.84	21.4	.242	6.1	6.3	1.1	.40	10	2.5	11	.20	5.1	0.027	0.7	7.50	SST	CG	N
0.296	7.52	AA-60	.84	21.4	.202	5.1	36	6.3	.23	5.9	8.4	37	.61	15.5	0.047	1.2	13.0	SST	CG	N
0.296	7.52	A12-8	.88	22.2	.270	6.9	.32	.06	.76	19	.24	1.1	.11	2.9	0.013	0.3	7.75	MW	C	N
0.296	7.52	EE-63	.88	22.2	.260	6.6	.73	.13	.65	17	.48	2.1	.23	5.7	0.018	0.5	11.5	MW	C	N
0.296	7.52	GG-93	.88	22.2	.260	6.6	.60	.11	.64	16	.39	1.7	.23	5.9	0.018	0.5	12.0	SST	C	N
0.296	7.52	BB-100	.88	22.2	.258	6.6	1.0	.18	.68	17	.68	3.0	.20	5.1	0.019	0.5	9.50	SST	C	N
0.296	7.52	2782	.88	22.2	.256	6.5	2.2	.38	.54	14	1.2	5.2	.16	4.1	0.020	0.5	7.00	HD	C	Z
0.296	7.52	B14-16	.88	22.2	.256	6.5	2.7	.48	.60	15	1.6	7.2	.12	3.0	0.020	0.5	6.00	MW	CG	N
0.296	7.52	S-1288	.88	22.2	.256	6.5	2.1	.37	.52	13	1.1	4.8	.15	3.8	0.020	0.5	6.50	SST	C	N
0.296	7.52	A13-6	.88	22.2	.250	6.4	4.3	.76	.57	14	2.5	11	.15	3.8	0.023	0.6	6.50	MW	CG	N
0.296	7.52	HH-51	.88	22.2	.248	6.3	2.1	.38	.58	15	1.2	5.5	.30	7.6	0.024	0.6	11.5	SST	C	N
0.296	7.52	A10-60	.88	22.2	.244	6.2	4.5	.79	.50	13	2.2	10	.22	5.6	0.026	0.7	8.50	SST	CG	N
0.296	7.52	GG-2	.88	22.2	.236	6.0	9.1	1.6	.37	9.5	3.4	15	.24	6.1	0.030	0.8	8.00	SST	CG	N
0.296	7.52	B1-12	.88	22.2	.232	5.9	13	2.2	.48	12	6.2	27	.27	6.8	0.032	0.8	8.33	MW	CG	N
0.296	7.52	AA-50	.88	22.2	.220	5.6	20	3.5	.33	8.3	6.6	29	.40	10.1	0.038	1.0	9.50	SST	C	N
0.296	7.52	2812	.88	22.2	.214	5.4	24	4.2	.34	8.7	8.3	37	.53	13.5	0.041	1.0	12.0	HD	C	Z
0.296	7.52	A11-29	.88	22.2	.212	5.4	31	5.4	.28	7.2	8.8	39	.41	10.4	0.042	1.1	9.75	SST	CG	N
0.296	7.52	B11-40	.88	22.2	.208	5.3	42	7.4	.26	6.5	11	48	.44	11.2	0.044	1.1	10.0	SPR	CG	N
0.296	7.52	K-4	.88	22.2	.206	5.2	38	6.6	.28	7.2	11	48	.47	12.0	0.045	1.1	10.5	SST	CG	N
0.296	7.52	F-34	.88	22.2	.204	5.2	56	9.8	.22	5.5	12	54	.47	12.0	0.046	1.2	9.25	SPR	C	Z
0.296	7.52	B11-48	.88	22.2	.204	5.2	37	6.6	.28	7.0	10	46	.60	15.2	0.046	1.2	13.0	SPR	CG	N
0.296	7.52	V-4	.91	23.0	.172	4.4	221	39	.12	3.1	27	119	.59	15.0	0.062	1.6	9.50	SPR	CG	N
0.296	7.52	GG-50	.94	23.8	.266	6.8	.47	.08	.80	20	.38	1.7	.14	3.4	0.015	0.4	8.00	SST	C	N
0.296	7.52	Z-5	.94	23.8	.234	5.9	7.8	1.4	.60	15	4.7	21	.34	8.7	0.031	0.8	11.0	MW	CG	Z
0.296	7.52	S-1497	.94	23.8	.220	5.6	19	3.4	.34	8.6	6.6	29	.37	9.4	0.038	1.0	9.75	SST	CG	N
0.296	7.52	JJ-42	.94	23.8	.216	5.5	27	4.8	.30	7.5	8.1	36	.40	10.2	0.040	1.0	10.0	SPR	CG	N
0.296	7.52	JJ-13	.94	23.8	.216	5.5	16	2.8	.34	8.6	5.5	24	.60	15.2	0.040	1.0	14.0	SST	C	N
0.296	7.52	A14-31	.94	23.8	.202	5.1	44	7.7	.28	7.0	12	54	.52	13.1	0.047	1.2	11.0	SST	CG	N
0.296	7.52	3667	.97	24.6	.230	5.8	12	2.0	.58	15	6.7	30	.36	9.2	0.033	0.8	10.0	MW	C	Z
0.296	7.52	A15-64	.97	24.6	.230	5.8	13	2.3	.37	9.3	4.9	22	.33	8.4	0.033	0.8	9.00	SPR	C	N
0.296	7.52	B14-32	.97	24.6	.222	5.6	19	3.4	.33	8.5	6.5	29	.37	9.4	0.037	0.9	10.0	SPR	CG	N
0.296	7.52	B11-30	.97	24.6	.220	5.6	22	3.8	.32	8.2	7.0	31	.38	9.7	0.038	1.0	10.0	SPR	C	N
0.296	7.52	B2-29	.98	25.0	.210	5.3	36	6.3	.28	7.1	10	45	.45	11.5	0.043	1.1	10.5	SPR	CG	N
0.296	7.52	Z-76	1.00	25.4	.272	6.9	.29	.05	.87	22	.25	1.1	.08	2.1	0.012	0.3	6.00	SST	C	N
0.296	7.52	10266	1.00	25.4	.266	6.8	.51	.09	.86	22	.43	1.9	.14	3.6	0.015	0.4	8.50	MW	C	Z
0.296	7.52	PP-81	1.00	25.4	.250	6.4	.89	.16	.49	13	.44	2.0	.51	12.9	0.023	0.6	21.0	SST	C	N
0.296	7.52	Z-49	1.00	25.4	.246	6.2	3.7	.65	.53	14	2.0	8.9	.24	6.0	0.025	0.6	8.50	SST	C	N
0.296	7.52	G-62	1.00	25.4	.244	6.2	3.3	.59	.67	17	2.2	9.9	.33	8.5	0.026	0.7	11.9	MW	C	Z
0.296	7.52	JJ-43	1.00	25.4	.242	6.1	4.9	.85	.70	18	3.4	15	.30	7.5	0.027	0.7	10.0	MW	C	N
0.296	7.52	2643	1.00	25.4	.240	6.1	3.0	.52	.49	12	1.5	6.5	.51	13.0	0.028	0.7	17.3	MW	C	Z
0.296	7.52	3763	1.00	25.4	.236	6.0	12	2.1	.42	11	5.1	23	.24	6.1	0.030	0.8	7.00	MW	C	Z
0.296	7.52	3875	1.00	25.4	.236	6.0	7.6	1.3	.67	17	5.1	23	.33	8.4	0.030	0.8	10.0	MW	C	Z
0.296	7.52	2666	1.00	25.4	.232	5.9	9.0	1.6	.62	16	5.5	25	.38	9.8	0.032	0.8	11.0	MW	C	Z
0.296	7.52	B9-43	1.00	25.4	.226	5.7	15	2.7	.34	8.5	5.2	23	.32	8.0	0.035	0.9	9.00	SST	CG	N
0.296	7.52	S-230	1.00	25.4	.224	5.7	14	2.4	.40	10	5.6	25	.38	9.6	0.036	0.9	10.5	SST	CG	N
0.296	7.52	M-87	1.00	25.4	.206	5.2	34	5.9	.32	8.1	11	48	.56	14.3	0.045	1.1	11.5	SST	C	N
0.296	7.52	UU-46	1.00	25.4	.206	5.2	43	7.6	.26	6.7	11	51	.52	13.1	0.045	1.1	10.5	SPR	C	N
0.296	7.52	S-10	1.00	25.4	.202	5.1	33	5.7	.30	7.5	9.6	43	.71	17.9	0.047	1.2	14.0	SST	C	N
0.296	7.52	L-55	1.00	25.4	.196	5.0	52	9.1	.28	7.1	14	64	.68	17.1	0.050	1.3	13.5	SPR	CG	N
0.296	7.52	KK-33	1.00	25.4	.186	4.7	77	13	.23	5.9	18	80	.74	18.9	0.055	1.4	12.5	SST	C	N
0.296	7.52	G-49	1.00	25.4	.172	4.4	242	42	.11	2.8	27	119	.54	13.8	0.062	1.6	8.75	SPR	CG	Z
0.296	7.52	S-1306	1.03	26.2	.220	5.6	20	3.5	.33	8.3	6.6	29	.36	9.2	0.038	1.0	9.50	SST	CG	N
0.296	7.52	S-37	1.03	26.2	.152	3.9	365	64	.10	2.5	36	159	.81	20.6	0.072	1.8	10.3	SST	C	N
0.296	7.52	M-112	1.06	27.0	.254	6.5	1.5	.26	.81	21	1.2	5.3	.25	6.4	0.021	0.5	11.0	MW	C	Z
0.296	7.52	A15-29	1.06	27.0	.250	6.4	1.1	.19	.65	17	.72	3.2	.41	10.4	0.023	0.6	17.8	SST	CG	N
0.296	7.52	JJ-19	1.06	27.0	.176	4.5	105	18	.22	5.6	23	102	.84	21.3	0.060	1.5	14.0	SST	CG	N
0.296	7.52	S-1088	1.13	28.6	.268	6.8	.10	.02	.79	20	.08	.35	.34	8.5	0.014	0.4	23.0	SST	C	N
0.296	7.52	H-53	1.13	28.6	.252	6.4	1.8	.31	.82	21	1.4	6.4	.24	6.1	0.022	0.6	10.0	SST	C	N
0.296	7.52	CC-29	1.13	28.6	.248	6.3	2.5	.43	.83	21	2.0	9.1	.30	7.6	0.024	0.6	11.5	MW	C	Z
0.296	7.52	10627	1.13	28.6	.232	5.9	7.1	1.2	.69	18	4.9	22	.43	11.0	0.032	0.8	13.5	MW	CG	Z
0.296	7.52	S-1117	1.13	28.6	.232	5.9	8.8	1.5	.47	12	4.1	18	.35	8.9	0.032	0.8	10.0	SST	C	N
0.296	7.52	3628	1.13	28.6	.220	5.6	18	3.2	.53	14	9.7	43	.44	11.1	0.038	1.0	11.5	MW	CG	Z
0.296	7.52	S-793	1.13	28.6	.220	5.6	16	2.8	.42	11	6.6	29	.44	11.1	0.038	1.0	11.5	SST	CG	N
0.296	7.52	MM-31	1.13	28.6	.216	5.5	16	2.8	.47	12	7.6	34	.60	15.2	0.040	1.0	14.0	SST	C	N
0.296	7.52	A11-42	1.13	28.6	.210	5.3	30	5.3	.33	8.5	10	45	.52	13.1	0.043	1.1	12.0	SPR	CG	GI
0.296	7.52	B8-31	1.16	29.4	.234	5.9	9.0	1.6	.42	11	3.8	17	.28	7.1	0.031	0.8	9.00	SST	CG	N
0.296	7.52	B9-45	1.19	30.2	.256	6.5	1.3	.23	.98	25	1.3	5.6	.21	5.3	0.020	0.5	10.5	MW	CG	N
0.296	7.52	3219	1.19	30.2	.254	6.5	1.4	.25	.93	24	1.3	6.0	.26	6.5	0.021	0.5	11.3	MW	C	Z
0.296	7.52	QQ-46	1.19	30.2	.236	6.0	4.7	.82	.71	18	3.3	15	.48	12.2	0.030					



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.296	7.52	M-96	1.28	32.5	.182	4.6	129	23	.16	4.1	21	94	.60	15.2	0.057	1.4	10.5	SPR	CG	Z
0.296	7.52	B7-9	1.31	33.3	.244	6.2	3.7	.65	.90	23	3.3	15	.29	7.3	0.026	0.7	11.0	MW	CG	N
0.296	7.52	S-3076	1.31	33.3	.238	6.0	5.4	.95	.57	15	3.1	14	.33	8.5	0.029	0.7	10.5	SST	CG	N
0.296	7.52	I-77	1.31	33.3	.206	5.2	32	5.7	.35	9.0	11	51	.61	15.4	0.045	1.1	13.5	SPR	CG	N
0.296	7.52	AA-57	1.31	33.3	.176	4.5	98	17	.25	6.3	24	108	.99	25.1	0.060	1.5	16.5	SPR	CG	N
0.296	7.52	VW-56	1.38	34.9	.258	6.6	1.2	.22	1.1	29	1.4	6.2	.19	4.8	0.019	0.5	9.00	MW	C	Z
0.296	7.52	3855	1.38	34.9	.240	6.1	4.3	.76	.96	24	4.2	19	.38	9.6	0.028	0.7	12.5	MW	C	Z
0.296	7.52	KK-28	1.38	34.9	.236	6.0	6.2	1.1	.82	21	5.1	23	.36	9.1	0.030	0.8	12.0	MW	CG	GI
0.296	7.52	4319	1.38	34.9	.234	5.9	4.7	.82	.82	21	3.8	17	.56	14.2	0.031	0.8	17.0	MW	C	Z
0.296	7.52	A13-46	1.38	34.9	.218	5.5	15	2.6	.48	12	7.1	31	.54	13.6	0.039	1.0	13.8	SST	CG	N
0.296	7.52	A12-70	1.38	34.9	.218	5.5	20	3.4	.53	14	10	47	.51	12.9	0.039	1.0	12.0	MW	C	Z
0.296	7.52	2889	1.38	34.9	.214	5.4	16	2.8	.54	14	8.7	39	.74	18.7	0.041	1.0	17.0	SPR	CG	Z
0.296	7.52	B15-57	1.38	34.9	.210	5.3	24	4.3	.41	11	10	45	.62	15.8	0.043	1.1	14.5	SPR	CG	Z
0.296	7.52	A11-13	1.38	34.9	.200	5.1	34	5.9	.38	9.7	13	58	.72	18.3	0.048	1.2	15.0	SST	CG	N
0.296	7.52	11405	1.41	35.7	.248	6.3	2.6	.46	1.1	27	2.8	12	.29	7.3	0.024	0.6	11.0	MW	C	Z
0.296	7.52	Q-54	1.44	36.5	.202	5.1	28	4.9	.44	11	12	54	.75	19.1	0.047	1.2	16.0	SST	CG	N
0.296	7.52	K-86	1.44	36.5	.196	5.0	40	7.0	.34	8.7	14	61	.75	19.1	0.050	1.3	15.0	SST	CG	N
0.296	7.52	H-83	1.50	38.1	.256	6.5	.72	.13	1.2	30	.85	3.8	.32	8.1	0.020	0.5	15.0	SST	C	N
0.296	7.52	4280	1.50	38.1	.238	6.0	4.1	.71	1.0	26	4.2	19	.46	11.8	0.029	0.7	15.0	MW	C	Z
0.296	7.52	11408	1.50	38.1	.226	5.7	8.8	1.5	.86	22	7.6	34	.59	14.9	0.035	0.9	15.8	MW	C	Z
0.296	7.52	B9-10	1.50	38.1	.226	5.7	9.3	1.6	.59	15	5.5	25	.53	13.3	0.035	0.9	15.0	SPR	CG	N
0.296	7.52	11900	1.50	38.1	.222	5.6	11	1.9	.55	14	6.1	27	.54	13.6	0.037	0.9	14.5	SST	CG	N
0.296	7.52	A13-8	1.50	38.1	.212	5.4	17	3.0	.50	13	8.8	39	.66	16.8	0.042	1.1	15.8	SST	CG	N
0.296	7.52	10057	1.50	38.1	.206	5.2	26	4.6	.44	11	11	51	.77	19.4	0.045	1.1	16.0	SPR	C	GI
0.296	7.52	A14-36	1.50	38.1	.206	5.2	23	4.1	.46	12	11	48	.72	18.3	0.045	1.1	16.0	SST	CG	N
0.296	7.52	2840	1.63	41.3	.228	5.8	5.9	1.0	.95	24	5.6	25	.68	17.2	0.034	0.9	19.9	MW	CG	Z
0.296	7.52	S-1558	1.63	41.3	.228	5.8	4.5	.79	.83	21	3.7	17	.80	20.3	0.034	0.9	22.5	SPR	C	N
0.296	7.52	3532	1.66	42.1	.222	5.6	9.3	1.6	.70	18	6.5	29	.68	17.4	0.037	0.9	18.5	SPR	CG	GI
0.296	7.52	A-37	1.69	42.8	.170	4.3	105	18	.26	6.7	28	124	1.26	32.0	0.063	1.6	19.0	HD	C	N
0.296	7.52	U-36	1.72	43.6	.224	5.7	8.6	1.5	.70	18	6.0	27	.65	16.5	0.036	0.9	18.0	SPR	CG	GI
0.296	7.52	F-29	1.72	43.6	.172	4.4	126	22	.21	5.4	27	119	.99	25.2	0.062	1.6	15.0	SPR	C	Z
0.296	7.52	S-1433	1.75	44.5	.256	6.5	.99	.17	1.1	28	1.1	4.8	.25	6.4	0.020	0.5	11.5	SST	C	N
0.296	7.52	10203	1.75	44.5	.252	6.4	1.9	.34	1.1	29	2.2	9.6	.23	5.9	0.022	0.6	10.5	MW	CG	Z
0.296	7.52	AA-55	1.75	44.5	.246	6.2	2.5	.44	1.2	30	3.0	13	.35	8.9	0.025	0.6	13.0	MW	C	Z
0.296	7.52	QQ-64	1.75	44.5	.246	6.2	1.6	.28	1.2	31	2.0	8.8	.51	13.0	0.025	0.6	19.5	MW	C	Z
0.296	7.52	3603	1.75	44.5	.232	5.9	6.6	1.2	.93	24	6.2	27	.49	12.4	0.032	0.8	14.3	MW	C	Z
0.296	7.52	B12-15	1.78	45.2	.214	5.4	16	2.7	.56	14	8.7	39	.73	18.5	0.041	1.0	17.8	SPR	CG	N
0.296	7.52	1747	1.81	46.0	.244	6.2	3.3	.58	1.0	25	3.3	15	.34	8.6	0.026	0.7	12.0	MW	C	Z
0.296	7.52	M-124	1.88	47.6	.218	5.5	12	2.2	.61	15	7.6	34	.72	18.3	0.039	1.0	17.5	SPR	C	GI
0.296	7.52	3366	1.88	47.6	.216	5.5	14	2.4	.81	20	11	50	.74	18.8	0.040	1.0	17.5	MW	C	Z
0.296	7.52	2633	1.88	47.6	.172	4.4	109	19	.34	8.6	37	165	1.05	26.8	0.062	1.6	17.0	MW	CG	Z
0.296	7.52	11476	1.94	49.2	.236	6.0	4.4	.77	1.2	29	5.1	23	.51	13.0	0.030	0.8	16.0	MW	CG	GI
0.296	7.52	A10-68	1.94	49.2	.212	5.4	13	2.3	.66	17	8.8	39	.84	21.3	0.042	1.1	20.0	SST	CG	N
0.296	7.52	B4-14	1.95	49.6	.172	4.4	111	19	.24	6.1	27	119	1.12	28.3	0.062	1.6	17.0	SPR	C	N
0.296	7.52	S-1006	2.00	50.8	.234	5.9	3.5	.61	1.1	27	3.8	17	.64	16.1	0.031	0.8	19.5	SST	C	N
0.296	7.52	10071	2.00	50.8	.208	5.3	18	3.2	.58	15	11	48	.88	22.4	0.044	1.1	20.0	SPR	CG	Z
0.296	7.52	B10-7	2.09	53.2	.218	5.5	10	1.8	.74	19	7.6	34	.83	21.1	0.039	1.0	21.3	SPR	CG	N
0.296	7.52	B15-62	2.16	54.8	.204	5.2	17	3.0	.71	18	12	54	1.24	31.5	0.046	1.2	26.0	SPR	C	N
0.296	7.52	S-1026	2.16	54.8	.202	5.1	16	2.8	.75	19	12	54	1.27	32.2	0.047	1.2	26.0	SST	C	N
0.296	7.52	S-880	2.28	57.9	.238	6.0	1.4	.25	1.3	32	1.8	8.1	1.02	25.8	0.029	0.7	34.0	SST	C	N
0.296	7.52	Q-15	2.56	65.1	.218	5.5	9.6	1.7	.79	20	7.6	34	.88	22.3	0.039	1.0	22.5	SPR	CG	N
0.296	7.52	3651	2.56	65.1	.200	5.1	16	2.9	.84	21	14	61	1.54	39.0	0.048	1.2	32.0	SPR	CG	Z
0.296	7.52	S-1127	2.63	66.7	.224	5.7	5.8	1.0	.97	25	5.6	25	.85	21.5	0.036	0.9	22.5	SST	C	N
0.296	7.52	B8-18	2.75	69.9	.244	6.2	2.6	.45	1.3	33	3.3	15	.39	9.9	0.026	0.7	15.0	MW	CG	N
0.296	7.52	10625	2.75	69.9	.176	4.5	33	5.8	.74	19	24	108	1.50	38.1	0.060	1.5	25.0	PB	CG	N
0.296	7.52	S-190	2.78	70.6	.202	5.1	12	2.0	1.1	27	12	54	1.72	43.6	0.047	1.2	36.5	SST	CG	Z
0.296	7.52	2531	3.00	76.2	.226	5.7	3.2	.56	1.6	40	5.0	22	1.44	36.4	0.035	0.9	40.0	MW	C	Z
0.296	7.52	S-1441	3.00	76.2	.200	5.1	13	2.3	.99	25	13	58	1.68	42.7	0.048	1.2	35.0	SST	CG	N
0.296	7.52	S-1581	3.25	82.6	.204	5.2	11	1.9	1.0	26	11	51	1.62	41.2	0.046	1.2	35.3	SST	CG	N
0.296	7.52	S-1014	3.41	86.5	.202	5.1	16	2.7	.78	20	12	54	1.32	33.4	0.047	1.2	27.0	SST	C	N
0.296	7.52	10647	3.88	98.4	.236	6.0	2.0	.36	2.5	63	5.1	23	.99	25.1	0.030	0.8	33.0	MW	C	Z
0.296	7.52	2570	7.50	190.5	.224	5.7	2.0	.35	3.0	76	6.0	27	2.59	65.8	0.036	0.9	71.0	SPR	C	Z
0.296	7.52	10513	7.50	190.5	.214	5.4	3.6	.62	2.5	62	8.7	39	2.90	73.7	0.041	1.0	70.8	SPR	CG	N
0.300	7.62	B4-65	.34	8.7	.254	6.5	4.7	.82	.22	5.5	1.0	4.5	.13	3.2	0.023	0.6	5.50	SST	CG	N
0.300	7.62	70779	.38	9.7	.256	6.5	8.6	1.5	.25	6.3	2.1	9.5	.09	2.2	0.022	0.6	3.88	MW	CG	N
0.300	7.62	70779S	.38	9.7	.256	6.5	7.3	1.3	.19	4.9	1.4	6.3	.09	2.2	0.022	0.6	3.88	SST	CG	N
0.300	7.62	70802	.38	9.7	.248	6.3	15	2.7	.21	5.4	3.3	15	.11	2.7	0.026	0.7	4.13	MW	CG	N
0.300	7.62	70802S	.38	9.7	.248	6.3	13	2.3	.17	4.3	2.2	9								





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70944	.38	9.7	.210	5.3	124	22	.13	3.2	16	70	.22	5.6	0.045	1.1	4.88	MW	CG	N
0.300	7.62	70944S	.38	9.7	.210	5.3	105	18	.10	2.6	11	47	.22	5.6	0.045	1.1	4.88	SST	CG	N
0.300	7.62	70963	.38	9.7	.206	5.2	159	28	.11	2.8	18	79	.22	5.7	0.047	1.2	4.75	MW	CG	N
0.300	7.62	70963S	.38	9.7	.206	5.2	135	24	.09	2.3	12	53	.22	5.7	0.047	1.2	4.75	SST	CG	N
0.300	7.62	70984	.38	9.7	.202	5.1	190	33	.11	2.7	20	89	.23	5.9	0.049	1.2	4.75	MW	CG	N
0.300	7.62	70984S	.38	9.7	.202	5.1	161	28	.08	2.1	14	60	.23	5.9	0.049	1.2	4.75	SST	CG	N
0.300	7.62	71005	.38	9.7	.198	5.0	228	40	.09	2.3	21	94	.24	6.2	0.051	1.3	4.75	MW	CG	N
0.300	7.62	71005S	.38	9.7	.198	5.0	194	34	.07	1.9	14	63	.24	6.2	0.051	1.3	4.75	SST	CG	N
0.300	7.62	70780	.44	11.2	.256	6.5	7.2	1.3	.30	7.5	2.1	9.5	.09	2.3	0.022	0.6	4.13	MW	CG	N
0.300	7.62	70780S	.44	11.2	.256	6.5	6.1	1.1	.23	5.9	1.4	6.3	.09	2.3	0.022	0.6	4.13	SST	CG	N
0.300	7.62	70803	.44	11.2	.248	6.3	13	2.3	.25	6.4	3.3	15	.11	2.9	0.026	0.7	4.38	MW	CG	N
0.300	7.62	70803S	.44	11.2	.248	6.3	11	2.0	.20	5.0	2.2	9.8	.11	2.9	0.026	0.7	4.38	SST	CG	N
0.300	7.62	70826	.44	11.2	.240	6.1	21	3.6	.24	6.2	5.0	22	.15	3.7	0.030	0.8	4.88	MW	CG	N
0.300	7.62	70826S	.44	11.2	.240	6.1	18	3.1	.19	4.9	3.4	15	.15	3.7	0.030	0.8	4.88	SST	CG	N
0.300	7.62	70848	.44	11.2	.236	6.0	27	4.8	.22	5.7	6.1	27	.16	4.0	0.032	0.8	4.88	MW	CG	N
0.300	7.62	70848S	.44	11.2	.236	6.0	23	4.0	.18	4.5	4.1	18	.16	4.0	0.032	0.8	4.88	SST	CG	N
0.300	7.62	70869	.44	11.2	.230	5.8	38	6.7	.20	5.0	7.5	34	.18	4.4	0.035	0.9	5.00	MW	CG	N
0.300	7.62	70869S	.44	11.2	.230	5.8	33	5.7	.16	4.0	5.1	23	.18	4.4	0.035	0.9	5.00	SST	CG	N
0.300	7.62	70888	.44	11.2	.224	5.7	53	9.3	.18	4.6	9.6	43	.19	4.9	0.038	1.0	5.13	MW	CG	N
0.300	7.62	70888S	.44	11.2	.224	5.7	45	7.9	.14	3.6	6.5	29	.19	4.9	0.038	1.0	5.13	SST	CG	N
0.300	7.62	70907	.44	11.2	.220	5.6	65	11	.17	4.3	11	50	.21	5.3	0.040	1.0	5.25	MW	CG	N
0.300	7.62	70907S	.44	11.2	.220	5.6	56	9.7	.14	3.4	7.5	33	.21	5.3	0.040	1.0	5.25	SST	CG	N
0.300	7.62	70926	.44	11.2	.216	5.5	89	16	.14	3.6	13	57	.20	5.2	0.042	1.1	4.88	MW	CG	N
0.300	7.62	70926S	.44	11.2	.216	5.5	76	13	.11	2.9	8.7	39	.20	5.2	0.042	1.1	4.88	SST	CG	N
0.300	7.62	70945	.44	11.2	.210	5.3	105	18	.15	3.8	16	70	.24	6.1	0.045	1.1	5.38	MW	CG	N
0.300	7.62	70945S	.44	11.2	.210	5.3	89	16	.12	3.0	11	47	.24	6.1	0.045	1.1	5.38	SST	CG	N
0.300	7.62	70964	.44	11.2	.206	5.2	132	23	.13	3.4	18	79	.25	6.3	0.047	1.2	5.25	MW	CG	N
0.300	7.62	70964S	.44	11.2	.206	5.2	112	20	.11	2.7	12	53	.25	6.3	0.047	1.2	5.25	SST	CG	N
0.300	7.62	70985	.44	11.2	.202	5.1	156	27	.13	3.3	20	89	.26	6.7	0.049	1.2	5.38	MW	CG	N
0.300	7.62	70985S	.44	11.2	.202	5.1	133	23	.10	2.6	14	60	.26	6.7	0.049	1.2	5.38	SST	CG	N
0.300	7.62	71006	.44	11.2	.198	5.0	187	33	.11	2.9	21	94	.27	7.0	0.051	1.3	5.38	MW	CG	N
0.300	7.62	71006S	.44	11.2	.198	5.0	159	28	.09	2.3	14	63	.27	7.0	0.051	1.3	5.38	SST	CG	N
0.300	7.62	B4-69	.47	11.9	.258	6.6	2.7	.47	.31	7.8	.83	3.7	.16	4.1	0.021	0.5	6.75	MW	C	GI
0.300	7.62	70781	.50	12.7	.256	6.5	6.6	1.1	.33	8.3	2.1	9.5	.10	2.4	0.022	0.6	4.38	MW	CG	N
0.300	7.62	70781S	.50	12.7	.256	6.5	5.6	.97	.25	6.5	1.4	6.3	.10	2.4	0.022	0.6	4.38	SST	CG	N
0.300	7.62	70804	.50	12.7	.248	6.3	11	2.0	.29	7.4	3.3	15	.13	3.2	0.026	0.7	4.88	MW	CG	N
0.300	7.62	70804S	.50	12.7	.248	6.3	9.6	1.7	.23	5.8	2.2	9.8	.13	3.2	0.026	0.7	4.88	SST	CG	N
0.300	7.62	70827	.50	12.7	.240	6.1	18	3.1	.28	7.2	5.0	22	.16	4.1	0.030	0.8	5.38	MW	CG	N
0.300	7.62	70827S	.50	12.7	.240	6.1	15	2.6	.22	5.7	3.4	15	.16	4.1	0.030	0.8	5.38	SST	CG	N
0.300	7.62	70849	.50	12.7	.236	6.0	23	4.1	.26	6.6	6.1	27	.17	4.4	0.032	0.8	5.38	MW	CG	N
0.300	7.62	70849S	.50	12.7	.236	6.0	20	3.5	.21	5.2	4.1	18	.17	4.4	0.032	0.8	5.38	SST	CG	N
0.300	7.62	70870	.50	12.7	.230	5.8	33	5.8	.23	5.8	7.5	34	.19	4.9	0.035	0.9	5.50	MW	CG	N
0.300	7.62	70870S	.50	12.7	.230	5.8	28	4.9	.18	4.6	5.1	23	.19	4.9	0.035	0.9	5.50	SST	CG	N
0.300	7.62	70889	.50	12.7	.224	5.7	46	8.1	.21	5.3	9.6	43	.21	5.4	0.038	1.0	5.63	MW	CG	N
0.300	7.62	70889S	.50	12.7	.224	5.7	39	6.9	.17	4.2	6.5	29	.21	5.4	0.038	1.0	5.63	SST	CG	N
0.300	7.62	70908	.50	12.7	.220	5.6	55	9.7	.20	5.1	11	50	.23	5.8	0.040	1.0	5.75	MW	CG	N
0.300	7.62	70908S	.50	12.7	.220	5.6	47	8.3	.16	4.1	7.5	33	.23	5.8	0.040	1.0	5.75	SST	CG	N
0.300	7.62	70927	.50	12.7	.216	5.5	70	12	.18	4.6	13	57	.24	6.1	0.042	1.1	5.75	MW	CG	N
0.300	7.62	70927S	.50	12.7	.216	5.5	60	10	.15	3.7	8.7	39	.24	6.1	0.042	1.1	5.75	SST	CG	N
0.300	7.62	70946	.50	12.7	.210	5.3	91	16	.17	4.4	16	70	.26	6.7	0.045	1.1	5.88	MW	CG	N
0.300	7.62	70946S	.50	12.7	.210	5.3	78	14	.14	3.5	11	47	.26	6.7	0.045	1.1	5.88	SST	CG	N
0.300	7.62	70965	.50	12.7	.206	5.2	112	20	.16	4.0	18	79	.28	7.0	0.047	1.2	5.88	MW	CG	N
0.300	7.62	70965S	.50	12.7	.206	5.2	95	17	.13	3.2	12	53	.28	7.0	0.047	1.2	5.88	SST	CG	N
0.300	7.62	70986	.50	12.7	.202	5.1	133	23	.15	3.8	20	89	.29	7.5	0.049	1.2	6.00	MW	CG	N
0.300	7.62	70986S	.50	12.7	.202	5.1	113	20	.12	3.0	14	60	.29	7.5	0.049	1.2	6.00	SST	CG	N
0.300	7.62	71007	.50	12.7	.198	5.0	158	28	.13	3.4	21	94	.31	7.8	0.051	1.3	6.00	MW	CG	N
0.300	7.62	71007S	.50	12.7	.198	5.0	134	24	.11	2.7	14	63	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.300	7.62	70782	.56	14.2	.256	6.5	6.0	1.0	.36	9.1	2.1	9.5	.10	2.6	0.022	0.6	4.63	MW	CG	N
0.300	7.62	70782S	.56	14.2	.256	6.5	5.1	.89	.28	7.1	1.4	6.3	.10	2.6	0.022	0.6	4.63	SST	CG	N
0.300	7.62	70805	.56	14.2	.248	6.3	10	1.8	.33	8.3	3.3	15	.13	3.4	0.026	0.7	5.13	MW	CG	N
0.300	7.62	70805S	.56	14.2	.248	6.3	8.6	1.5	.26	6.5	2.2	9.8	.13	3.4	0.026	0.7	5.13	SST	CG	N
0.300	7.62	70828	.56	14.2	.240	6.1	16	2.7	.32	8.1	5.0	22	.17	4.4	0.030	0.8	5.75	MW	CG	N
0.300	7.62	70828S	.56	14.2	.240	6.1	13	2.3	.25	6.4	3.4	15	.17	4.4	0.030	0.8	5.75	SST	CG	N
0.300	7.62	70850	.56	14.2	.236	6.0	20	3.5	.30	7.7	6.1	27	.19	4.8	0.032	0.8	5.88	MW	CG	N
0.300	7.62	70850S	.56	14.2	.236	6.0	17	3.0	.24	6.0	4.1	18	.19	4.8	0.032	0.8	5.88	SST	CG	N
0.300	7.62	70871	.56	14.2	.230	5.8	29	5.0	.26	6.7	7.5	34	.21	5.3	0.035	0.9	6.00	MW	CG	N
0.300	7.62	70871S	.56	14.2	.230	5.8	24	4.3	.21	5.3	5.1	23	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.300	7.62	70890	.56	14.2	.224	5.7	39	6.8	.25	6.3	9.6	43	.24	6.0	0.038	1.0	6.25	MW	CG	N
0.300	7.62	70890S	.56	14.2	.224	5.7	33	5.8	.20	5.0	6									




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	71008S	.56	14.2	.198	5.0	116	20	.12	3.1	14	63	.34	8.6	0.051	1.3	6.63	SST	CG	N
0.300	7.62	B4-34	.56	14.3	.224	5.7	37	6.5	.26	6.6	9.6	43	.25	6.3	0.038	1.0	6.50	MW	CG	GI
0.300	7.62	70783	.63	16.0	.256	6.5	5.0	.88	.43	11	2.1	9.5	.11	2.9	0.022	0.6	5.13	MW	CG	N
0.300	7.62	70783S	.63	16.0	.256	6.5	4.3	.74	.33	8.5	1.4	6.3	.11	2.9	0.022	0.6	5.13	SST	CG	N
0.300	7.62	70806	.63	16.0	.248	6.3	9.0	1.6	.37	9.4	3.3	15	.15	3.7	0.026	0.7	5.63	MW	CG	N
0.300	7.62	70806S	.63	16.0	.248	6.3	7.6	1.3	.29	7.4	2.2	9.8	.15	3.7	0.026	0.7	5.63	SST	CG	N
0.300	7.62	70829	.63	16.0	.240	6.1	14	2.4	.36	9.2	5.0	22	.19	4.8	0.030	0.8	6.25	MW	CG	N
0.300	7.62	70829S	.63	16.0	.240	6.1	12	2.1	.28	7.2	3.4	15	.19	4.8	0.030	0.8	6.25	SST	CG	N
0.300	7.62	70851	.63	16.0	.236	6.0	18	3.2	.34	8.5	6.1	27	.20	5.2	0.032	0.8	6.38	MW	CG	N
0.300	7.62	70851S	.63	16.0	.236	6.0	15	2.7	.26	6.7	4.1	18	.20	5.2	0.032	0.8	6.38	SST	CG	N
0.300	7.62	70872	.63	16.0	.230	5.8	26	4.5	.29	7.5	7.5	34	.23	5.8	0.035	0.9	6.50	MW	CG	N
0.300	7.62	70872S	.63	16.0	.230	5.8	22	3.8	.23	6.0	5.1	23	.23	5.8	0.035	0.9	6.50	SST	CG	N
0.300	7.62	70891	.63	16.0	.224	5.7	35	6.1	.27	7.0	9.6	43	.26	6.5	0.038	1.0	6.75	MW	CG	N
0.300	7.62	70891S	.63	16.0	.224	5.7	30	5.2	.22	5.5	6.5	29	.26	6.5	0.038	1.0	6.75	SST	CG	N
0.300	7.62	70910	.63	16.0	.220	5.6	43	7.5	.26	6.6	11	50	.28	7.0	0.040	1.0	6.88	MW	CG	N
0.300	7.62	70910S	.63	16.0	.220	5.6	37	6.4	.21	5.2	7.5	33	.28	7.0	0.040	1.0	6.88	SST	CG	N
0.300	7.62	70929	.63	16.0	.216	5.5	52	9.1	.25	6.3	13	57	.29	7.5	0.042	1.1	7.00	MW	CG	N
0.300	7.62	70929S	.63	16.0	.216	5.5	44	7.7	.20	5.0	8.7	39	.29	7.5	0.042	1.1	7.00	SST	CG	N
0.300	7.62	70948	.63	16.0	.210	5.3	68	12	.23	5.8	16	70	.33	8.3	0.045	1.1	7.25	MW	CG	N
0.300	7.62	70948S	.63	16.0	.210	5.3	58	10	.18	4.6	11	47	.33	8.3	0.045	1.1	7.25	SST	CG	N
0.300	7.62	70967	.63	16.0	.206	5.2	86	15	.21	5.2	18	79	.33	8.4	0.047	1.2	7.00	MW	CG	N
0.300	7.62	70967S	.63	16.0	.206	5.2	73	13	.16	4.2	12	53	.33	8.4	0.047	1.2	7.00	SST	CG	N
0.300	7.62	70988	.63	16.0	.202	5.1	102	18	.20	5.0	20	89	.35	8.9	0.049	1.2	7.13	MW	CG	N
0.300	7.62	70988S	.63	16.0	.202	5.1	87	15	.16	4.0	14	60	.35	8.9	0.049	1.2	7.13	SST	CG	N
0.300	7.62	71009	.63	16.0	.198	5.0	121	21	.17	4.4	21	94	.37	9.4	0.051	1.3	7.25	MW	CG	N
0.300	7.62	71009S	.63	16.0	.198	5.0	103	18	.14	3.5	14	63	.37	9.4	0.051	1.3	7.25	SST	CG	N
0.300	7.62	70784	.69	17.5	.256	6.5	4.6	.81	.46	12	2.1	9.5	.12	3.0	0.022	0.6	5.38	MW	CG	N
0.300	7.62	70784S	.69	17.5	.256	6.5	3.9	.68	.36	9.2	1.4	6.3	.12	3.0	0.022	0.6	5.38	SST	CG	N
0.300	7.62	70807	.69	17.5	.248	6.3	7.9	1.4	.42	11	3.3	15	.16	4.0	0.026	0.7	6.00	MW	CG	N
0.300	7.62	70807S	.69	17.5	.248	6.3	6.7	1.2	.33	8.4	2.2	9.8	.16	4.0	0.026	0.7	6.00	SST	CG	N
0.300	7.62	70823	.69	17.5	.242	6.1	9.0	1.6	.47	12	4.2	19	.22	5.6	0.029	0.7	7.63	MW	CG	N
0.300	7.62	70823S	.69	17.5	.242	6.1	7.7	1.3	.40	10	3.1	14	.22	5.6	0.029	0.7	7.63	SST	CG	N
0.300	7.62	70830	.69	17.5	.240	6.1	13	2.2	.40	10	5.0	22	.20	5.1	0.030	0.8	6.75	MW	CG	N
0.300	7.62	70830S	.69	17.5	.240	6.1	11	1.9	.32	8.1	3.4	15	.20	5.1	0.030	0.8	6.75	SST	CG	N
0.300	7.62	70852	.69	17.5	.236	6.0	16	2.8	.38	9.6	6.1	27	.22	5.6	0.032	0.8	6.88	MW	CG	N
0.300	7.62	70852S	.69	17.5	.236	6.0	14	2.4	.30	7.5	4.1	18	.22	5.6	0.032	0.8	6.88	SST	CG	N
0.300	7.62	70873	.69	17.5	.230	5.8	23	4.0	.33	8.4	7.5	34	.25	6.3	0.035	0.9	7.13	MW	CG	N
0.300	7.62	70873S	.69	17.5	.230	5.8	19	3.4	.26	6.7	5.1	23	.25	6.3	0.035	0.9	7.13	SST	CG	N
0.300	7.62	70892	.69	17.5	.224	5.7	30	5.3	.32	8.1	9.6	43	.29	7.2	0.038	1.0	7.50	MW	CG	N
0.300	7.62	70892S	.69	17.5	.224	5.7	26	4.5	.25	6.4	6.5	29	.29	7.2	0.038	1.0	7.50	SST	CG	N
0.300	7.62	70911	.69	17.5	.220	5.6	38	6.7	.29	7.4	11	50	.30	7.6	0.040	1.0	7.50	MW	CG	N
0.300	7.62	70911S	.69	17.5	.220	5.6	32	5.7	.23	5.9	7.5	33	.30	7.6	0.040	1.0	7.50	SST	CG	N
0.300	7.62	70930	.69	17.5	.216	5.5	46	8.0	.28	7.2	13	57	.33	8.3	0.042	1.1	7.75	MW	CG	N
0.300	7.62	70930S	.69	17.5	.216	5.5	39	6.8	.22	5.7	8.7	39	.33	8.3	0.042	1.1	7.75	SST	CG	N
0.300	7.62	70949	.69	17.5	.210	5.3	62	11	.25	6.5	16	70	.35	8.9	0.045	1.1	7.75	MW	CG	N
0.300	7.62	70949S	.69	17.5	.210	5.3	52	9.2	.20	5.2	11	47	.35	8.9	0.045	1.1	7.75	SST	CG	N
0.300	7.62	70968	.69	17.5	.206	5.2	77	13	.23	5.9	18	79	.36	9.1	0.047	1.2	7.63	MW	CG	N
0.300	7.62	70968S	.69	17.5	.206	5.2	65	11	.18	4.7	12	53	.36	9.1	0.047	1.2	7.63	SST	CG	N
0.300	7.62	70989	.69	17.5	.202	5.1	90	16	.22	5.6	20	89	.38	9.6	0.049	1.2	7.75	MW	CG	N
0.300	7.62	70989S	.69	17.5	.202	5.1	77	13	.18	4.5	14	60	.38	9.6	0.049	1.2	7.75	SST	CG	N
0.300	7.62	71010	.69	17.5	.198	5.0	107	19	.20	5.0	21	94	.40	10.2	0.051	1.3	7.88	MW	CG	N
0.300	7.62	71010S	.69	17.5	.198	5.0	91	16	.16	4.0	14	63	.40	10.2	0.051	1.3	7.88	SST	CG	N
0.300	7.62	70785	.75	19.1	.256	6.5	4.1	.71	.53	13	2.1	9.5	.13	3.3	0.022	0.6	5.88	MW	CG	N
0.300	7.62	70785S	.75	19.1	.256	6.5	3.4	.60	.41	10	1.4	6.3	.13	3.3	0.022	0.6	5.88	SST	CG	N
0.300	7.62	70808	.75	19.1	.248	6.3	7.5	1.3	.44	11	3.3	15	.16	4.1	0.026	0.7	6.25	MW	CG	N
0.300	7.62	70808S	.75	19.1	.248	6.3	6.3	1.1	.35	8.9	2.2	9.8	.16	4.1	0.026	0.7	6.25	SST	CG	N
0.300	7.62	70831	.75	19.1	.240	6.1	11	2.0	.44	11	5.0	22	.21	5.4	0.030	0.8	7.13	MW	CG	N
0.300	7.62	70831S	.75	19.1	.240	6.1	9.7	1.7	.35	8.8	3.4	15	.21	5.4	0.030	0.8	7.13	SST	CG	N
0.300	7.62	70853	.75	19.1	.236	6.0	15	2.6	.41	10	6.1	27	.23	5.9	0.032	0.8	7.25	MW	CG	N
0.300	7.62	70853S	.75	19.1	.236	6.0	13	2.2	.32	8.1	4.1	18	.23	5.9	0.032	0.8	7.25	SST	CG	N
0.300	7.62	70874	.75	19.1	.230	5.8	21	3.6	.36	9.2	7.5	34	.27	6.8	0.035	0.9	7.63	MW	CG	N
0.300	7.62	70874S	.75	19.1	.230	5.8	18	3.1	.29	7.3	5.1	23	.27	6.8	0.035	0.9	7.63	SST	CG	N
0.300	7.62	70893	.75	19.1	.224	5.7	28	4.9	.34	8.7	9.6	43	.30	7.7	0.038	1.0	8.00	MW	CG	N
0.300	7.62	70893S	.75	19.1	.224	5.7	24	4.2	.27	6.9	6.5	29	.30	7.7	0.038	1.0	8.00	SST	CG	N
0.300	7.62	70912	.75	19.1	.220	5.6	34	6.0	.32	8.2	11	50	.33	8.3	0.040	1.0	8.13	MW	CG	N
0.300	7.62	70912S	.75	19.1	.220	5.6	29	5.1	.26	6.5	7.5	33	.33	8.3	0.040	1.0	8.13	SST	CG	N
0.300	7.62	70931	.75	19.1	.216	5.5	42	7.3	.31	7.8	13	57	.35	8.8	0.042	1.1	8.25	MW	CG	N
0.300	7.62	70931S	.75	19.1	.216	5.5	36	6.2	.24	6.2	8.7	39	.35	8.8	0.042	1.1	8.25	SST	CG	N
0.300	7.62	70950	.75	19.1	.210</															



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70832	.81	20.6	.240	6.1	10	1.8	.48	12	5.0	22	.23	5.8	0.030	0.8	7.63	MW	CG	N
0.300	7.62	70832S	.81	20.6	.240	6.1	8.9	1.6	.38	9.6	3.4	15	.23	5.8	0.030	0.8	7.63	SST	CG	N
0.300	7.62	70854	.81	20.6	.236	6.0	14	2.4	.45	11	6.1	27	.25	6.3	0.032	0.8	7.75	MW	CG	N
0.300	7.62	70854S	.81	20.6	.236	6.0	12	2.0	.35	9.0	4.1	18	.25	6.3	0.032	0.8	7.75	SST	CG	N
0.300	7.62	70875	.81	20.6	.230	5.8	19	3.3	.40	10	7.5	34	.28	7.2	0.035	0.9	8.13	MW	CG	N
0.300	7.62	70875S	.81	20.6	.230	5.8	16	2.8	.31	8.0	5.1	23	.28	7.2	0.035	0.9	8.13	SST	CG	N
0.300	7.62	70894	.81	20.6	.224	5.7	26	4.5	.37	9.4	9.6	43	.32	8.1	0.038	1.0	8.38	MW	CG	N
0.300	7.62	70894S	.81	20.6	.224	5.7	22	3.9	.29	7.5	6.5	29	.32	8.1	0.038	1.0	8.38	SST	CG	N
0.300	7.62	70913	.81	20.6	.220	5.6	32	5.5	.35	9.0	11	50	.35	8.8	0.040	1.0	8.63	MW	CG	N
0.300	7.62	70913S	.81	20.6	.220	5.6	27	4.7	.28	7.1	7.5	33	.35	8.8	0.040	1.0	8.63	SST	CG	N
0.300	7.62	70932	.81	20.6	.216	5.5	38	6.6	.34	8.6	13	57	.37	9.5	0.042	1.1	8.88	MW	CG	N
0.300	7.62	70932S	.81	20.6	.216	5.5	32	5.6	.27	6.9	8.7	39	.37	9.5	0.042	1.1	8.88	SST	CG	N
0.300	7.62	70951	.81	20.6	.210	5.3	51	9.0	.31	7.8	16	70	.41	10.3	0.045	1.1	9.00	MW	CG	N
0.300	7.62	70951S	.81	20.6	.210	5.3	43	7.6	.24	6.2	11	47	.41	10.3	0.045	1.1	9.00	SST	CG	N
0.300	7.62	70970	.81	20.6	.206	5.2	63	11	.28	7.1	18	79	.42	10.6	0.047	1.2	8.88	MW	CG	N
0.300	7.62	70970S	.81	20.6	.206	5.2	54	9.4	.22	5.7	12	53	.42	10.6	0.047	1.2	8.88	SST	CG	N
0.300	7.62	70991	.81	20.6	.202	5.1	75	13	.27	6.8	20	89	.44	11.2	0.049	1.2	9.00	MW	CG	N
0.300	7.62	70991S	.81	20.6	.202	5.1	64	11	.21	5.4	14	60	.44	11.2	0.049	1.2	9.00	SST	CG	N
0.300	7.62	71012	.81	20.6	.198	5.0	89	16	.24	6.0	21	94	.47	11.8	0.051	1.3	9.13	MW	CG	N
0.300	7.62	71012S	.81	20.6	.198	5.0	75	13	.19	4.8	14	63	.47	11.8	0.051	1.3	9.13	SST	CG	N
0.300	7.62	70787	.88	22.4	.256	6.5	3.3	.58	.65	16	2.1	9.5	.15	3.8	0.022	0.6	6.75	MW	CG	N
0.300	7.62	70787S	.88	22.4	.256	6.5	2.8	.49	.51	13	1.4	6.3	.15	3.8	0.022	0.6	6.75	SST	CG	N
0.300	7.62	70810	.88	22.4	.248	6.3	6.1	1.1	.55	14	3.3	15	.19	4.8	0.026	0.7	7.25	MW	CG	N
0.300	7.62	70810S	.88	22.4	.248	6.3	5.1	.90	.43	11	2.2	9.8	.19	4.8	0.026	0.7	7.25	SST	CG	N
0.300	7.62	70833	.88	22.4	.240	6.1	9.7	1.7	.52	13	5.0	22	.24	6.2	0.030	0.8	8.13	MW	CG	N
0.300	7.62	70833S	.88	22.4	.240	6.1	8.2	1.4	.41	10	3.4	15	.24	6.2	0.030	0.8	8.13	SST	CG	N
0.300	7.62	70855	.88	22.4	.236	6.0	12	2.2	.49	13	6.1	27	.27	6.8	0.032	0.8	8.38	MW	CG	N
0.300	7.62	70855S	.88	22.4	.236	6.0	10	1.8	.39	9.9	4.1	18	.27	6.8	0.032	0.8	8.38	SST	CG	N
0.300	7.62	70876	.88	22.4	.230	5.8	18	3.1	.43	11	7.5	34	.30	7.7	0.035	0.9	8.63	MW	CG	N
0.300	7.62	70876S	.88	22.4	.230	5.8	15	2.6	.34	8.7	5.1	23	.30	7.7	0.035	0.9	8.63	SST	CG	N
0.300	7.62	70895	.88	22.4	.224	5.7	23	4.0	.41	11	9.6	43	.35	8.9	0.038	1.0	9.25	MW	CG	N
0.300	7.62	70895S	.88	22.4	.224	5.7	20	3.4	.33	8.4	6.5	29	.35	8.9	0.038	1.0	9.25	SST	CG	N
0.300	7.62	70914	.88	22.4	.220	5.6	29	5.1	.38	9.7	11	50	.37	9.3	0.040	1.0	9.13	MW	CG	N
0.300	7.62	70914S	.88	22.4	.220	5.6	25	4.3	.30	7.7	7.5	33	.37	9.3	0.040	1.0	9.13	SST	CG	N
0.300	7.62	70933	.88	22.4	.216	5.5	34	5.9	.38	9.6	13	57	.40	10.3	0.042	1.1	9.63	MW	CG	N
0.300	7.62	70933S	.88	22.4	.216	5.5	29	5.0	.30	7.7	8.7	39	.40	10.3	0.042	1.1	9.63	SST	CG	N
0.300	7.62	70952	.88	22.4	.210	5.3	46	8.1	.34	8.6	16	70	.44	11.1	0.045	1.1	9.75	MW	CG	N
0.300	7.62	70952S	.88	22.4	.210	5.3	39	6.9	.27	6.9	11	47	.44	11.1	0.045	1.1	9.75	SST	CG	N
0.300	7.62	70971	.88	22.4	.206	5.2	58	10	.31	7.8	18	79	.45	11.3	0.047	1.2	9.50	MW	CG	N
0.300	7.62	70971S	.88	22.4	.206	5.2	49	8.6	.24	6.2	12	53	.45	11.3	0.047	1.2	9.50	SST	CG	N
0.300	7.62	70992	.88	22.4	.202	5.1	68	12	.29	7.4	20	89	.47	12.0	0.049	1.2	9.63	MW	CG	N
0.300	7.62	70992S	.88	22.4	.202	5.1	58	10	.23	5.9	14	60	.47	12.0	0.049	1.2	9.63	SST	CG	N
0.300	7.62	71013	.88	22.4	.198	5.0	81	14	.26	6.6	21	94	.50	12.6	0.051	1.3	9.75	MW	CG	N
0.300	7.62	71013S	.88	22.4	.198	5.0	69	12	.21	5.3	14	63	.50	12.6	0.051	1.3	9.75	SST	CG	N
0.300	7.62	70789	.94	23.9	.256	6.5	3.3	.58	.65	16	2.1	9.5	.15	3.8	0.022	0.6	6.75	MW	CG	N
0.300	7.62	70789S	.94	23.9	.256	6.5	2.8	.49	.51	13	1.4	6.3	.15	3.8	0.022	0.6	6.75	SST	CG	N
0.300	7.62	70811	.94	23.9	.248	6.3	5.5	.96	.60	15	3.3	15	.20	5.1	0.026	0.7	7.75	MW	CG	N
0.300	7.62	70811S	.94	23.9	.248	6.3	4.7	.82	.47	12	2.2	9.8	.20	5.1	0.026	0.7	7.75	SST	CG	N
0.300	7.62	70834	.94	23.9	.240	6.1	9.0	1.6	.56	14	5.0	22	.26	6.6	0.030	0.8	8.63	MW	CG	N
0.300	7.62	70834S	.94	23.9	.240	6.1	7.6	1.3	.44	11	3.4	15	.26	6.6	0.030	0.8	8.63	SST	CG	N
0.300	7.62	70856	.94	23.9	.236	6.0	11	2.0	.55	14	6.1	27	.29	7.3	0.032	0.8	9.00	MW	CG	N
0.300	7.62	70856S	.94	23.9	.236	6.0	9.5	1.7	.43	11	4.1	18	.29	7.3	0.032	0.8	9.00	SST	CG	N
0.300	7.62	70877	.94	23.9	.230	5.8	16	2.8	.46	12	7.5	34	.32	8.1	0.035	0.9	9.13	MW	CG	N
0.300	7.62	70877S	.94	23.9	.230	5.8	14	2.4	.37	9.4	5.1	23	.32	8.1	0.035	0.9	9.13	SST	CG	N
0.300	7.62	70896	.94	23.9	.224	5.7	22	3.8	.44	11	9.6	43	.37	9.3	0.038	1.0	9.63	MW	CG	N
0.300	7.62	70896S	.94	23.9	.224	5.7	19	3.3	.35	8.8	6.5	29	.37	9.3	0.038	1.0	9.63	SST	CG	N
0.300	7.62	70915	.94	23.9	.220	5.6	27	4.8	.41	10	11	50	.39	9.9	0.040	1.0	9.75	MW	CG	N
0.300	7.62	70915S	.94	23.9	.220	5.6	23	4.0	.33	8.3	7.5	33	.39	9.9	0.040	1.0	9.75	SST	CG	N
0.300	7.62	70934	.94	23.9	.216	5.5	32													




1-800-237-5225
1-213-749-1466
Fax (213)749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70916	1.00	25.4	.220	5.6	25	4.4	.44	11	11	50	.41	10.4	0.040	1.0	10.3	MW	CG	N
0.300	7.62	70916S	1.00	25.4	.220	5.6	22	3.8	.35	8.9	7.5	33	.41	10.4	0.040	1.0	10.3	SST	CG	N
0.300	7.62	70935	1.00	25.4	.216	5.5	30	5.3	.43	11	13	57	.45	11.3	0.042	1.1	10.6	MW	CG	N
0.300	7.62	70935S	1.00	25.4	.216	5.5	26	4.5	.34	8.6	8.7	39	.45	11.3	0.042	1.1	10.6	SST	CG	N
0.300	7.62	70954	1.00	25.4	.210	5.3	40	7.0	.39	9.9	16	70	.49	12.4	0.045	1.1	10.9	MW	CG	N
0.300	7.62	70954S	1.00	25.4	.210	5.3	34	6.0	.31	7.9	11	47	.49	12.4	0.045	1.1	10.9	SST	CG	N
0.300	7.62	70973	1.00	25.4	.206	5.2	50	8.8	.35	9.0	18	79	.50	12.7	0.047	1.2	10.6	MW	CG	N
0.300	7.62	70973S	1.00	25.4	.206	5.2	43	7.5	.28	7.2	12	53	.50	12.7	0.047	1.2	10.6	SST	CG	N
0.300	7.62	70994	1.00	25.4	.202	5.1	59	10	.34	8.6	20	89	.53	13.5	0.049	1.2	10.9	MW	CG	N
0.300	7.62	70994S	1.00	25.4	.202	5.1	50	8.8	.27	6.8	14	60	.53	13.5	0.049	1.2	10.9	SST	CG	N
0.300	7.62	71015	1.00	25.4	.198	5.0	70	12	.30	7.6	21	94	.56	14.2	0.051	1.3	11.0	MW	CG	N
0.300	7.62	71015S	1.00	25.4	.198	5.0	60	10	.24	6.1	14	63	.56	14.2	0.051	1.3	11.0	SST	CG	N
0.300	7.62	70792	1.13	28.7	.256	6.5	2.7	.47	.79	20	2.1	9.5	.17	4.3	0.022	0.6	7.75	MW	CG	N
0.300	7.62	70792S	1.13	28.7	.256	6.5	2.3	.40	.62	16	1.4	6.3	.17	4.3	0.022	0.6	7.75	SST	CG	N
0.300	7.62	70814	1.13	28.7	.248	6.3	4.6	.81	.72	18	3.3	15	.23	5.9	0.026	0.7	9.00	MW	CG	N
0.300	7.62	70814S	1.13	28.7	.248	6.3	3.9	.68	.57	14	2.2	9.8	.23	5.9	0.026	0.7	9.00	SST	CG	N
0.300	7.62	70837	1.13	28.7	.240	6.1	7.6	1.3	.66	17	5.0	22	.29	7.4	0.030	0.8	9.75	MW	CG	N
0.300	7.62	70837S	1.13	28.7	.240	6.1	6.5	1.1	.52	13	3.4	15	.29	7.4	0.030	0.8	9.75	SST	CG	N
0.300	7.62	70859	1.13	28.7	.236	6.0	9.5	1.7	.64	16	6.1	27	.33	8.3	0.032	0.8	10.3	MW	CG	N
0.300	7.62	70859S	1.13	28.7	.236	6.0	8.1	1.4	.50	13	4.1	18	.33	8.3	0.032	0.8	10.3	SST	CG	N
0.300	7.62	70879	1.13	28.7	.230	5.8	13	2.4	.56	14	7.5	34	.37	9.4	0.035	0.9	10.6	MW	CG	N
0.300	7.62	70879S	1.13	28.7	.230	5.8	11	2.0	.45	11	5.1	23	.37	9.4	0.035	0.9	10.6	SST	CG	N
0.300	7.62	70898	1.13	28.7	.224	5.7	19	3.3	.51	13	9.6	43	.41	10.5	0.038	1.0	10.9	MW	CG	N
0.300	7.62	70898S	1.13	28.7	.224	5.7	16	2.8	.41	10	6.5	29	.41	10.5	0.038	1.0	10.9	SST	CG	N
0.300	7.62	70917	1.13	28.7	.220	5.6	22	3.9	.50	13	11	50	.46	11.6	0.040	1.0	11.4	MW	CG	N
0.300	7.62	70917S	1.13	28.7	.220	5.6	19	3.3	.40	10	7.5	33	.46	11.6	0.040	1.0	11.4	SST	CG	N
0.300	7.62	70936	1.13	28.7	.216	5.5	28	4.8	.47	12	13	57	.48	12.3	0.042	1.1	11.5	MW	CG	N
0.300	7.62	70936S	1.13	28.7	.216	5.5	23	4.1	.37	9.4	8.7	39	.48	12.3	0.042	1.1	11.5	SST	CG	N
0.300	7.62	70955	1.13	28.7	.210	5.3	36	6.3	.43	11	16	70	.53	13.6	0.045	1.1	11.9	MW	CG	N
0.300	7.62	70955S	1.13	28.7	.210	5.3	31	5.4	.35	8.8	11	47	.53	13.6	0.045	1.1	11.9	SST	CG	N
0.300	7.62	70974	1.13	28.7	.206	5.2	44	7.7	.40	10	18	79	.55	14.0	0.047	1.2	11.8	MW	CG	N
0.300	7.62	70974S	1.13	28.7	.206	5.2	38	6.6	.32	8.1	12	53	.55	14.0	0.047	1.2	11.8	SST	CG	N
0.300	7.62	70995	1.13	28.7	.202	5.1	52	9.2	.38	9.7	20	89	.59	14.9	0.049	1.2	12.0	MW	CG	N
0.300	7.62	70995S	1.13	28.7	.202	5.1	44	7.8	.30	7.7	14	60	.59	14.9	0.049	1.2	12.0	SST	CG	N
0.300	7.62	71016	1.13	28.7	.198	5.0	62	11	.34	8.7	21	94	.62	15.9	0.051	1.3	12.3	MW	CG	N
0.300	7.62	71016S	1.13	28.7	.198	5.0	52	9.2	.27	6.9	14	63	.62	15.9	0.051	1.3	12.3	SST	CG	N
0.300	7.62	70793	1.25	31.8	.256	6.5	2.4	.42	.89	23	2.1	9.5	.19	4.7	0.022	0.6	8.50	MW	CG	N
0.300	7.62	70793S	1.25	31.8	.256	6.5	2.0	.36	.70	18	1.4	6.3	.19	4.7	0.022	0.6	8.50	SST	CG	N
0.300	7.62	70815	1.25	31.8	.248	6.3	4.3	.75	.77	19	3.3	15	.24	6.2	0.026	0.7	9.38	MW	CG	N
0.300	7.62	70815S	1.25	31.8	.248	6.3	3.7	.64	.60	15	2.2	9.8	.24	6.2	0.026	0.7	9.38	SST	CG	N
0.300	7.62	70838	1.25	31.8	.240	6.1	6.6	1.2	.76	19	5.0	22	.33	8.4	0.030	0.8	11.0	MW	CG	N
0.300	7.62	70838S	1.25	31.8	.240	6.1	5.6	.98	.60	15	3.4	15	.33	8.4	0.030	0.8	11.0	SST	CG	N
0.300	7.62	70860	1.25	31.8	.236	6.0	8.6	1.5	.71	18	6.1	27	.36	9.0	0.032	0.8	11.1	MW	CG	N
0.300	7.62	70860S	1.25	31.8	.236	6.0	7.3	1.3	.56	14	4.1	18	.36	9.0	0.032	0.8	11.1	SST	CG	N
0.300	7.62	70880	1.25	31.8	.230	5.8	12	2.1	.63	16	7.5	34	.41	10.4	0.035	0.9	11.8	MW	CG	N
0.300	7.62	70880S	1.25	31.8	.230	5.8	10	1.8	.50	13	5.1	23	.41	10.4	0.035	0.9	11.8	SST	CG	N
0.300	7.62	70899	1.25	31.8	.224	5.7	16	2.9	.59	15	9.6	43	.47	11.8	0.038	1.0	12.3	MW	CG	N
0.300	7.62	70899S	1.25	31.8	.224	5.7	14	2.4	.47	12	6.5	29	.47	11.8	0.038	1.0	12.3	SST	CG	N
0.300	7.62	70918	1.25	31.8	.220	5.6	20	3.4	.57	14	11	50	.51	12.8	0.040	1.0	12.6	MW	CG	N
0.300	7.62	70918S	1.25	31.8	.220	5.6	17	2.9	.45	11	7.5	33	.51	12.8	0.040	1.0	12.6	SST	CG	N
0.300	7.62	70937	1.25	31.8	.216	5.5	24	4.2	.53	14	13	57	.54	13.7	0.042	1.1	12.9	MW	CG	N
0.300	7.62	70937S	1.25	31.8	.216	5.5	20	3.6	.42	11	8.7	39	.54	13.7	0.042	1.1	12.9	SST	CG	N
0.300	7.62	70956	1.25	31.8	.210	5.3	32	5.6	.49	12	16	70	.59	14.9	0.045	1.1	13.0	MW	CG	N
0.300	7.62	70956S	1.25	31.8	.210	5.3	27	4.8	.39	9.9	11	47	.59	14.9	0.045	1.1	13.0	SST	CG	N
0.300	7.62	70975	1.25	31.8	.206	5.2	39	6.9	.45	11	18	79	.61	15.5	0.047	1.2	13.0	MW	CG	N
0.300	7.62	70975S	1.25	31.8	.206	5.2	36	5.9	.36	9.1	12	53	.61	15.5	0.047	1.2	13.0	SST	CG	N
0.300	7.62	70996	1.25	31.8	.202	5.1	46	8.1	.43	11	20	89	.65	16.5	0.049	1.2	13.3	MW	CG	N
0.300	7.62	70996S	1.25	31.8	.202	5.1	39	6.9	.34	8.7	14	60	.65	16.5	0.049	1.				



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70997	1.38	35.1	.202	5.1	42	7.3	.48	12	20	89	.72	18.2	0.049	1.2	14.6	MW	CG	N
0.300	7.62	70997S	1.38	35.1	.202	5.1	35	6.2	.38	9.7	14	60	.72	18.2	0.049	1.2	14.6	SST	CG	N
0.300	7.62	71018	1.38	35.1	.198	5.0	49	8.6	.43	11	21	94	.75	19.1	0.051	1.3	14.8	MW	CG	N
0.300	7.62	71018S	1.38	35.1	.198	5.0	42	7.3	.34	8.6	14	63	.75	19.1	0.051	1.3	14.8	SST	CG	N
0.300	7.62	70796	1.50	38.1	.256	6.5	2.1	.36	1.0	26	2.1	9.5	.21	5.4	0.022	0.6	9.63	MW	CG	N
0.300	7.62	70796S	1.50	38.1	.256	6.5	1.7	.31	.81	21	1.4	6.3	.21	5.4	0.022	0.6	9.63	SST	CG	N
0.300	7.62	70818	1.50	38.1	.248	6.3	3.5	.61	.94	24	3.3	15	.29	7.3	0.026	0.7	11.1	MW	CG	N
0.300	7.62	70818S	1.50	38.1	.248	6.3	3.0	.52	.74	19	2.2	9.8	.29	7.3	0.026	0.7	11.1	SST	CG	N
0.300	7.62	70841	1.50	38.1	.240	6.1	5.5	.95	.92	23	5.0	22	.39	9.8	0.030	0.8	12.9	MW	CG	N
0.300	7.62	70841S	1.50	38.1	.240	6.1	4.6	.81	.73	18	3.4	15	.39	9.8	0.030	0.8	12.9	SST	CG	N
0.300	7.62	70863	1.50	38.1	.236	6.0	7.1	1.2	.86	22	6.1	27	.42	10.7	0.032	0.8	13.1	MW	CG	N
0.300	7.62	70863S	1.50	38.1	.236	6.0	6.0	1.0	.68	17	4.1	18	.42	10.7	0.032	0.8	13.1	SST	CG	N
0.300	7.62	70882	1.50	38.1	.230	5.8	9.9	1.7	.76	19	7.5	34	.48	12.2	0.035	0.9	13.8	MW	CG	N
0.300	7.62	70882S	1.50	38.1	.230	5.8	8.4	1.5	.61	15	5.1	23	.48	12.2	0.035	0.9	13.8	SST	CG	N
0.300	7.62	70901	1.50	38.1	.224	5.7	14	2.4	.70	18	9.6	43	.54	13.6	0.038	1.0	14.1	MW	CG	N
0.300	7.62	70901S	1.50	38.1	.224	5.7	12	2.0	.56	14	6.5	29	.54	13.6	0.038	1.0	14.1	SST	CG	N
0.300	7.62	70920	1.50	38.1	.220	5.6	16	2.8	.70	18	11	50	.61	15.4	0.040	1.0	15.1	MW	CG	N
0.300	7.62	70920S	1.50	38.1	.220	5.6	14	2.4	.55	14	7.5	33	.61	15.4	0.040	1.0	15.1	SST	CG	N
0.300	7.62	70939	1.50	38.1	.216	5.5	20	3.5	.65	16	13	57	.64	16.1	0.042	1.1	15.1	MW	CG	N
0.300	7.62	70939S	1.50	38.1	.216	5.5	17	3.0	.51	13	8.7	39	.64	16.1	0.042	1.1	15.1	SST	CG	N
0.300	7.62	70958	1.50	38.1	.210	5.3	26	4.6	.60	15	16	70	.70	17.7	0.045	1.1	15.5	MW	CG	N
0.300	7.62	70958S	1.50	38.1	.210	5.3	22	3.9	.48	12	11	47	.70	17.7	0.045	1.1	15.5	SST	CG	N
0.300	7.62	12758	1.50	38.1	.206	5.2	27	4.8	.44	11	12	53	.74	18.8	0.047	1.2	15.8	SST	CG	N
0.300	7.62	70977	1.50	38.1	.206	5.2	32	5.7	.55	14	18	79	.72	18.4	0.047	1.2	15.4	MW	CG	N
0.300	7.62	70977S	1.50	38.1	.206	5.2	27	4.8	.44	11	12	53	.72	18.4	0.047	1.2	15.4	SST	CG	N
0.300	7.62	70998	1.50	38.1	.202	5.1	38	6.7	.53	13	20	89	.77	19.6	0.049	1.2	15.8	MW	CG	N
0.300	7.62	70998S	1.50	38.1	.202	5.1	32	5.7	.42	11	14	60	.77	19.6	0.049	1.2	15.8	SST	CG	N
0.300	7.62	71019	1.50	38.1	.198	5.0	45	7.9	.47	12	21	94	.82	20.7	0.051	1.3	16.0	MW	CG	N
0.300	7.62	71019S	1.50	38.1	.198	5.0	38	6.7	.37	9.5	14	63	.82	20.7	0.051	1.3	16.0	SST	CG	N
0.300	7.62	70797	1.75	44.5	.256	6.5	1.7	.30	1.2	31	2.1	9.5	.24	6.2	0.022	0.6	11.1	MW	CG	N
0.300	7.62	70797S	1.75	44.5	.256	6.5	1.5	.26	.97	25	1.4	6.3	.24	6.2	0.022	0.6	11.1	SST	CG	N
0.300	7.62	70819	1.75	44.5	.248	6.3	3.0	.53	1.1	28	3.3	15	.33	8.3	0.026	0.7	12.6	MW	CG	N
0.300	7.62	70819S	1.75	44.5	.248	6.3	2.6	.45	.87	22	2.2	9.8	.33	8.3	0.026	0.7	12.6	SST	CG	N
0.300	7.62	70842	1.75	44.5	.240	6.1	4.7	.81	1.1	27	5.0	22	.44	11.2	0.030	0.8	14.8	MW	CG	N
0.300	7.62	70842S	1.75	44.5	.240	6.1	4.0	.69	.85	22	3.4	15	.44	11.2	0.030	0.8	14.8	SST	CG	N
0.300	7.62	70864	1.75	44.5	.236	6.0	6.0	1.1	1.0	26	6.1	27	.48	12.2	0.032	0.8	15.0	MW	CG	N
0.300	7.62	70864S	1.75	44.5	.236	6.0	5.1	.89	.80	20	4.1	18	.48	12.2	0.032	0.8	15.0	SST	CG	N
0.300	7.62	70883	1.75	44.5	.230	5.8	8.4	1.5	.90	23	7.5	34	.55	14.0	0.035	0.9	15.8	MW	CG	N
0.300	7.62	70883S	1.75	44.5	.230	5.8	7.1	1.3	.71	18	5.1	23	.55	14.0	0.035	0.9	15.8	SST	CG	N
0.300	7.62	70902	1.75	44.5	.224	5.7	11	2.0	.85	22	9.6	43	.64	16.3	0.038	1.0	16.9	MW	CG	N
0.300	7.62	70902S	1.75	44.5	.224	5.7	9.5	1.7	.68	17	6.5	29	.64	16.3	0.038	1.0	16.9	SST	CG	N
0.300	7.62	70921	1.75	44.5	.220	5.6	14	2.4	.81	20	11	50	.69	17.4	0.040	1.0	17.1	MW	CG	N
0.300	7.62	70921S	1.75	44.5	.220	5.6	12	2.1	.64	16	7.5	33	.69	17.4	0.040	1.0	17.1	SST	CG	N
0.300	7.62	70940	1.75	44.5	.216	5.5	16	2.9	.78	20	13	57	.75	19.1	0.042	1.1	17.9	MW	CG	N
0.300	7.62	70940S	1.75	44.5	.216	5.5	14	2.4	.62	16	8.7	39	.75	19.1	0.042	1.1	17.9	SST	CG	N
0.300	7.62	70959	1.75	44.5	.210	5.3	22	3.8	.72	18	16	70	.83	21.0	0.045	1.1	18.4	MW	CG	N
0.300	7.62	70959S	1.75	44.5	.210	5.3	18	3.2	.57	15	11	47	.83	21.0	0.045	1.1	18.4	SST	CG	N
0.300	7.62	70978	1.75	44.5	.206	5.2	28	4.8	.65	16	18	79	.83	21.2	0.047	1.2	17.8	MW	CG	N
0.300	7.62	70978S	1.75	44.5	.206	5.2	23	4.1	.51	13	12	53	.83	21.2	0.047	1.2	17.8	SST	CG	N
0.300	7.62	70999	1.75	44.5	.202	5.1	32	5.7	.62	16	20	89	.89	22.6	0.049	1.2	18.1	MW	CG	N
0.300	7.62	70999S	1.75	44.5	.202	5.1	28	4.8	.49	13	14	60	.89	22.6	0.049	1.2	18.1	SST	CG	N
0.300	7.62	71020	1.75	44.5	.198	5.0	38	6.7	.55	14	21	94	.94	24.0	0.051	1.3	18.5	MW	CG	N
0.300	7.62	71020S	1.75	44.5	.198	5.0	32	5.7	.44	11	14	63	.94	24.0	0.051	1.3	18.5	SST	CG	N
0.300	7.62	70798	2.00	50.8	.256	6.5	1.5	.25	1.5	37	2.1	9.5	.28	7.1	0.022	0.6	12.8	MW	CG	N
0.300	7.62	70798S	2.00	50.8	.256	6.5	1.2	.22	1.2	29	1.4	6.3	.28	7.1	0.022	0.6	12.8	SST	CG	N
0.300	7.62	70820	2.00	50.8	.248	6.3	2.6	.46	1.3	32	3.3	15	.37	9.4	0.026	0.7	14.3	MW	CG	N
0.300	7.62	70820S	2.00	50.8	.248	6.3	2.2	.39	1.0	25	2.2	9.8	.37	9.4	0.026	0.7	14.3	SST	CG	N
0.300	7.62	70843	2.00	50.8	.240	6.1	4.0	.70	1.3	32	5.0	22	.50	12.8	0.030	0.8	16.8	MW	CG	N
0.300	7.62	70843S	2.00	50.8	.240	6.1	3.4	.60	.99	25	3.4	15	.50	12.8	0.030	0.8	16.8	SST	CG	N
0.300	7.62	70865	2.00	50.8	.236	6.0	5.3	.93	1.1	29	6.1	27	.54	13.6	0.032	0.8	16.8	MW	CG	N
0.300	7.62	70865S	2.00	50.8	.236	6.0	4.5	.79	.90	23	4.1	18	.54	13.6	0.032	0.8	16.8	SST	CG	N
0.300	7.62	70884	2.00	50.8	.230	5.8	7.3	1.3	1.0	26	7.5	34	.63	15.9	0.035	0.9	17.9	MW	CG	N
0.300	7.62	70884S	2.00	50.8	.230	5.8	6.2	1.1	.82	21	5.1	23	.63	15.9	0.035	0.9	17.9	SST	CG	N
0.300	7.62	70903	2.00	50.8	.224	5.7	9.6	1.7	1.0	25	9.6	43	.74	18.7	0.038	1.0	19.4	MW	CG	N
0.300	7.62	70903S	2.00	50.8	.224	5.7	8.2	1.4	.79	20	6.5	29	.74	18.7	0.038	1.0	19.4	SST	CG	N
0.300	7.62	70922	2.00	50.8	.220	5.6	12	2.1	.94	24	11	50	.79	19.9	0.040	1.0	19.6	MW	CG	N
0.300	7.62	70922S	2.00	50.8	.220	5.6	10	1.8	.74	19	7.5	33	.79	19.9	0.040	1.0	19.6	SST	CG	N
0.300	7.62	70941	2.00	50.8	.216	5.5	14	2.5	.89	23	13	57	.85	21.5	0.042	1.1	20.1	MW		




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.300	7.62	70821S	2.25	57.2	.248	6.3	2.0	.36	1.1	27	2.2	9.8	.40	10.1	0.026	0.7	15.3	SST	CG	N
0.300	7.62	70844	2.25	57.2	.240	6.1	3.6	.63	1.4	36	5.0	22	.56	14.2	0.030	0.8	18.6	MW	CG	N
0.300	7.62	70844S	2.25	57.2	.240	6.1	3.0	.53	1.1	28	3.4	15	.56	14.2	0.030	0.8	18.6	SST	CG	N
0.300	7.62	70866	2.25	57.2	.236	6.0	4.8	.84	1.3	32	6.1	27	.59	14.9	0.032	0.8	18.4	MW	CG	N
0.300	7.62	70866S	2.25	57.2	.236	6.0	4.1	.71	1.0	25	4.1	18	.59	14.9	0.032	0.8	18.4	SST	CG	N
0.300	7.62	70885	2.25	57.2	.230	5.8	6.5	1.1	1.2	30	7.5	34	.70	17.8	0.035	0.9	20.0	MW	CG	N
0.300	7.62	70885S	2.25	57.2	.230	5.8	5.5	.96	.93	24	5.1	23	.70	17.8	0.035	0.9	20.0	SST	CG	N
0.300	7.62	70904	2.25	57.2	.224	5.7	8.8	1.5	1.1	28	9.6	43	.80	20.3	0.038	1.0	21.0	MW	CG	N
0.300	7.62	70904S	2.25	57.2	.224	5.7	7.5	1.3	.87	22	6.5	29	.80	20.3	0.038	1.0	21.0	SST	CG	N
0.300	7.62	70923	2.25	57.2	.220	5.6	11	1.8	1.1	27	11	50	.88	22.2	0.040	1.0	21.9	MW	CG	N
0.300	7.62	70923S	2.25	57.2	.220	5.6	9.0	1.6	.84	21	7.5	33	.88	22.2	0.040	1.0	21.9	SST	CG	N
0.300	7.62	70942	2.25	57.2	.216	5.5	13	2.2	1.0	25	13	57	.94	23.9	0.042	1.1	22.4	MW	CG	N
0.300	7.62	70942S	2.25	57.2	.216	5.5	11	1.9	.80	20	8.7	39	.94	23.9	0.042	1.1	22.4	SST	CG	N
0.300	7.62	70961	2.25	57.2	.210	5.3	17	2.9	.93	24	16	70	1.04	26.4	0.045	1.1	23.1	MW	CG	N
0.300	7.62	70961S	2.25	57.2	.210	5.3	14	2.5	.74	19	11	47	1.04	26.4	0.045	1.1	23.1	SST	CG	N
0.300	7.62	70980	2.25	57.2	.206	5.2	21	3.7	.84	21	18	79	1.06	26.9	0.047	1.2	22.5	MW	CG	N
0.300	7.62	70980S	2.25	57.2	.206	5.2	18	3.1	.67	17	12	53	1.06	26.9	0.047	1.2	22.5	SST	CG	N
0.300	7.62	71001	2.25	57.2	.202	5.1	25	4.3	.81	21	20	89	1.13	28.8	0.049	1.2	23.1	MW	CG	N
0.300	7.62	71001S	2.25	57.2	.202	5.1	21	3.7	.64	16	14	60	1.13	28.8	0.049	1.2	23.1	SST	CG	N
0.300	7.62	71022	2.25	57.2	.198	5.0	29	5.1	.72	18	21	94	1.20	30.4	0.051	1.3	23.5	MW	CG	N
0.300	7.62	71022S	2.25	57.2	.198	5.0	25	4.4	.57	15	14	63	1.20	30.4	0.051	1.3	23.5	SST	CG	N
0.300	7.62	70800	2.50	63.5	.256	6.5	1.2	.21	1.8	46	2.1	9.5	.34	8.5	0.022	0.6	15.3	MW	CG	N
0.300	7.62	70800S	2.50	63.5	.256	6.5	1.0	.18	1.4	36	1.4	6.3	.34	8.5	0.022	0.6	15.3	SST	CG	N
0.300	7.62	70822	2.50	63.5	.248	6.3	2.1	.37	1.5	39	3.3	15	.44	11.1	0.026	0.7	16.9	MW	CG	N
0.300	7.62	70822S	2.50	63.5	.248	6.3	1.8	.32	1.2	31	2.2	9.8	.44	11.1	0.026	0.7	16.9	SST	CG	N
0.300	7.62	70845	2.50	63.5	.240	6.1	3.2	.57	1.6	39	5.0	22	.61	15.4	0.030	0.8	20.3	MW	CG	N
0.300	7.62	70845S	2.50	63.5	.240	6.1	2.8	.48	1.2	31	3.4	15	.61	15.4	0.030	0.8	20.3	SST	CG	N
0.300	7.62	70867	2.50	63.5	.236	6.0	4.3	.74	1.4	36	6.1	27	.65	16.6	0.032	0.8	20.4	MW	CG	N
0.300	7.62	70867S	2.50	63.5	.236	6.0	3.6	.63	1.1	29	4.1	18	.65	16.6	0.032	0.8	20.4	SST	CG	N
0.300	7.62	70886	2.50	63.5	.230	5.8	5.9	1.0	1.3	33	7.5	34	.77	19.4	0.035	0.9	21.9	MW	CG	N
0.300	7.62	70886S	2.50	63.5	.230	5.8	5.0	.87	1.0	26	5.1	23	.77	19.4	0.035	0.9	21.9	SST	CG	N
0.300	7.62	70905	2.50	63.5	.224	5.7	8.0	1.4	1.2	31	9.6	43	.87	22.2	0.038	1.0	23.0	MW	CG	N
0.300	7.62	70905S	2.50	63.5	.224	5.7	6.8	1.2	.96	24	6.5	29	.87	22.2	0.038	1.0	23.0	SST	CG	N
0.300	7.62	70924	2.50	63.5	.220	5.6	9.5	1.7	1.2	30	11	50	.96	24.4	0.040	1.0	24.0	MW	CG	N
0.300	7.62	70924S	2.50	63.5	.220	5.6	8.1	1.4	.93	24	7.5	33	.96	24.4	0.040	1.0	24.0	SST	CG	N
0.300	7.62	70943	2.50	63.5	.216	5.5	12	2.0	1.1	28	13	57	1.02	25.9	0.042	1.1	24.3	MW	CG	N
0.300	7.62	70943S	2.50	63.5	.216	5.5	9.9	1.7	.87	22	8.7	39	1.02	25.9	0.042	1.1	24.3	SST	CG	N
0.300	7.62	70962	2.50	63.5	.210	5.3	15	2.7	1.0	26	16	70	1.13	28.6	0.045	1.1	25.0	MW	CG	N
0.300	7.62	70962S	2.50	63.5	.210	5.3	13	2.3	.81	21	11	47	1.13	28.6	0.045	1.1	25.0	SST	CG	N
0.300	7.62	70981	2.50	63.5	.206	5.2	19	3.3	.94	24	18	79	1.17	29.7	0.047	1.2	24.9	MW	CG	N
0.300	7.62	70981S	2.50	63.5	.206	5.2	16	2.8	.75	19	12	53	1.17	29.7	0.047	1.2	24.9	SST	CG	N
0.300	7.62	71002	2.50	63.5	.202	5.1	22	3.9	.90	23	20	89	1.25	31.7	0.049	1.2	25.5	MW	CG	N
0.300	7.62	71002S	2.50	63.5	.202	5.1	19	3.3	.72	18	14	60	1.25	31.7	0.049	1.2	25.5	SST	CG	N
0.300	7.62	71023	2.50	63.5	.198	5.0	26	4.6	.80	20	21	94	1.33	33.7	0.051	1.3	26.0	MW	CG	N
0.300	7.62	71023S	2.50	63.5	.198	5.0	22	3.9	.64	16	14	63	1.33	33.7	0.051	1.3	26.0	SST	CG	N
0.300	7.62	70982	2.75	69.9	.206	5.2	17	3.0	1.0	26	18	79	1.29	32.7	0.047	1.2	27.4	MW	CG	N
0.300	7.62	70982S	2.75	69.9	.206	5.2	15	2.5	.83	21	12	53	1.29	32.7	0.047	1.2	27.4	SST	CG	N
0.300	7.62	71003	2.75	69.9	.202	5.1	20	3.5	.99	25	20	89	1.37	34.8	0.049	1.2	28.0	MW	CG	N
0.300	7.62	71003S	2.75	69.9	.202	5.1	17	3.0	.79	20	14	60	1.37	34.8	0.049	1.2	28.0	SST	CG	N
0.300	7.62	71024	2.75	69.9	.198	5.0	24	4.2	.88	22	21	94	1.45	36.9	0.051	1.3	28.5	MW	CG	N
0.300	7.62	71024S	2.75	69.9	.198	5.0	20	3.5	.71	18	14	63	1.45	36.9	0.051	1.3	28.5	SST	CG	N
0.300	7.62	12640	2.88	73.0	.260	6.6	.33	.06	2.3	57	.73	3.3	.62	15.7	0.020	0.5	30.0	SST	C	N
0.300	7.62	70983	3.00	76.2	.206	5.2	16	2.7	1.1	29	18	79	1.39	35.4	0.047	1.2	29.6	MW	CG	N
0.300	7.62	70983S	3.00	76.2	.206	5.2	13	2.3	.90	23	12	53	1.39	35.4	0.047	1.2	29.6	SST	CG	N
0.300	7.62	71004	3.00	76.2	.202	5.1	18	3.2	1.1	28	20	89	1.49	38.0	0.049	1.2	30.5	MW	CG	N
0.300	7.62	71004S	3.00	76.2	.202	5.1	16	2.7	.87	22	14	60	1.49	38.0	0.049	1.2	30.5	SST	CG	N
0.300	7.62	71025	3.00	76.2	.198	5.0	22	3.8	.97	25	21	94	1.58	40.2	0.051	1.3	31.0	MW	CG	N
0.300	7.62	71025S	3.00	76.2	.198	5.0	18	3.2	.77	20	14	63	1.58	40.2	0.051	1.3	31.0	SST	CG	N
0.304	7.72	A9-39	.78	19.8	.190	4.8	93	16	.22	5.6	21	92	.46	11.8	0.057	1.4	8.00	PB	CG	N
0.312	7.92	II-25	.19	4.8	.252	6.4	45	7.9	.07	1.7	3.1	14	.12	3.0	0.030	0.8	3.00	SST	C	N
0.312	7.92	KK-86	.22	5.6	.260	6.6	17	2.9	.10	2.6	1.7	7.5	.12	3.0	0.026	0.7	3.50	SST	C	N
0.312	7.92	NN-86	.25	6.4	.258	6.6	17	2.9	.12	2.9	1.9	8.4	.14	3.4	0.027	0.7	4.00	MW	C	N
0.312	7.92	A15-5	.25	6.4	.252	6.4	16	2.7	.10	2.5	1.6	7.0	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.312	7.92	EE-4	.25	6.4	.232	5.9	80	14	.09	2.3	7.2	32	.16	4.1	0.040	1.0	4.00	SST	CG	N
0.312	7.92	S-1267	.31	7.9	.288	7.3	.26	.04	.23	5.9	.06	.26	.08	2.1	0.012	0.3	5.75	SST	C	N
0.312	7.92	A-81	.31	7.9	.262	6.7	12	2.1	.19	4.7	2.2	9.9	.13	3.2	0.025	0.6	4.00	MW	C	Z
0.312	7.92	12482	.31	7.9	.248	6.3	46	8.0	.09	2.3	4.2	19	.14	3.7	0.032	0.8	3.50	SPR	C	N
0.312	7.92	GG-15	.31	7.9	.202	5.1	34													



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.312	7.92	EE-9	.38	9.5	.226	5.7	101	18	.09	2.4	9.6	43	.19	4.9	0.043	1.1	4.50	SPR	CG	Z
0.312	7.92	S-1086	.38	9.5	.218	5.5	131	23	.09	2.2	12	52	.21	5.4	0.047	1.2	4.50	SST	CG	N
0.312	7.92	K-93	.38	9.5	.218	5.5	94	17	.09	2.4	8.8	39	.28	7.2	0.047	1.2	6.00	SPR	CG	Z
0.312	7.92	S-1125	.38	9.5	.214	5.4	158	28	.08	2.1	13	58	.22	5.6	0.049	1.2	4.50	SST	CG	N
0.312	7.92	3688	.41	10.3	.272	6.9	2.3	.40	.27	6.8	.61	2.7	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.312	7.92	JJ-22	.41	10.3	.244	6.2	26	4.6	.18	4.5	4.7	21	.20	5.2	0.034	0.9	5.00	SST	C	N
0.312	7.92	FF-3	.44	11.1	.280	7.1	.91	.16	.33	8.3	.30	1.3	.11	2.8	0.016	0.4	6.00	MW	C	N
0.312	7.92	KK-92	.44	11.1	.252	6.4	11	2.0	.23	5.8	2.6	11	.21	5.3	0.030	0.8	6.00	SST	C	N
0.312	7.92	A11-23	.44	11.1	.246	6.2	26	4.6	.18	4.5	4.6	21	.17	4.3	0.033	0.8	5.00	SPR	CG	GI
0.312	7.92	A14-25	.44	11.1	.236	6.0	39	6.8	.16	4.1	6.24	27.72	.12	3.0	0.038	1.0	5.25	SST	CG	N
0.312	7.92	LL-16	.44	11.1	.232	5.9	41	7.1	.18	4.6	7.3	32	.24	6.1	0.040	1.0	6.00	SST	CG	N
0.312	7.92	S-484	.44	11.1	.230	5.8	43	7.5	.18	4.6	7.8	35	.25	6.4	0.041	1.0	6.13	SST	CG	N
0.312	7.92	B9-30	.44	11.1	.230	5.8	82	14	.10	2.6	8.3	37	.18	4.7	0.041	1.0	4.50	SPR	CG	N
0.312	7.92	H-96	.44	11.1	.212	5.4	167	29	.08	2.1	14	62	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.312	7.92	II-23	.44	11.1	.212	5.4	136	24	.10	2.4	13	58	.26	6.7	0.050	1.3	5.25	SST	CG	N
0.312	7.92	2920	.44	11.1	.180	4.6	697	122	.04	1.1	30	136	.31	7.8	0.066	1.7	4.63	SPR	CG	Z
0.312	7.92	NN-6	.47	11.9	.272	6.9	2.0	.36	.33	8.3	.67	3.0	.14	3.6	0.020	0.5	6.00	SST	C	N
0.312	7.92	J-27	.47	11.9	.252	6.4	11	2.0	.26	6.6	2.9	13	.21	5.3	0.030	0.8	6.00	SST	C	N
0.312	7.92	A10-36	.47	11.9	.250	6.4	18	3.1	.20	5.1	3.6	16	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.312	7.92	DD-85	.47	11.9	.242	6.1	29	5.2	.17	4.2	4.9	22	.21	5.3	0.035	0.9	5.00	SST	C	N
0.312	7.92	J-52	.47	11.9	.238	6.0	43	7.6	.14	3.6	6.2	27	.22	5.6	0.037	0.9	5.00	SPR	C	N
0.312	7.92	10487	.50	12.7	.284	7.2	1.0	.18	.43	11	.45	2.0	.07	1.8	0.014	0.4	4.00	MW	C	N
0.312	7.92	4231	.50	12.7	.282	7.2	.51	.09	.37	9.5	.19	.84	.13	3.2	0.015	0.4	7.50	MW	C	N
0.312	7.92	4199	.50	12.7	.276	7.0	1.2	.21	.36	9.0	.42	1.9	.14	3.7	0.018	0.5	7.00	MW	C	Z
0.312	7.92	H-69	.50	12.7	.272	6.9	1.4	.24	.32	8.1	.44	1.9	.18	4.6	0.020	0.5	8.00	SST	C	N
0.312	7.92	B14-5	.50	12.7	.270	6.9	2.3	.40	.35	9.0	.80	3.6	.15	3.7	0.021	0.5	7.00	MW	CG	N
0.312	7.92	S-727	.50	12.7	.268	6.8	4.8	.84	.28	7.2	1.4	6.1	.12	3.1	0.022	0.6	4.50	SST	C	N
0.312	7.92	B2-28	.50	12.7	.266	6.8	7.4	1.3	.32	8.0	2.3	10	.12	3.1	0.023	0.6	4.25	MW	C	N
0.312	7.92	PP-31	.50	12.7	.256	6.5	13	2.3	.31	7.8	4.0	18	.14	3.6	0.028	0.7	5.00	MW	CG	N
0.312	7.92	10229	.50	12.7	.248	6.3	17	3.0	.25	6.2	4.2	19	.22	5.7	0.032	0.8	6.00	SPR	C	Z
0.312	7.92	931	.50	12.7	.238	6.0	37	6.5	.23	5.9	8.5	38	.20	5.2	0.037	0.9	5.50	MW	CG	Z
0.312	7.92	L-8	.50	12.7	.236	6.0	42	7.4	.15	3.8	6.3	28	.23	5.8	0.038	1.0	5.00	SST	C	N
0.312	7.92	10856	.50	12.7	.230	5.8	51	8.9	.16	4.1	8.3	37	.25	6.2	0.041	1.0	6.00	SPR	CG	N
0.312	7.92	DD-34	.50	12.7	.192	4.9	291	51	.08	2.0	23	104	.36	9.1	0.060	1.5	6.00	SPR	CG	N
0.312	7.92	S-1265	.53	13.5	.238	6.0	28	4.9	.21	5.2	5.8	26	.26	6.6	0.037	0.9	6.00	SST	C	N
0.312	7.92	HH-29	.53	13.5	.232	5.9	36	6.3	.20	5.1	7.3	32	.26	6.6	0.040	1.0	6.50	SST	CG	N
0.312	7.92	CC-11	.53	13.5	.232	5.9	52	9.1	.15	3.8	7.8	35	.26	6.6	0.040	1.0	5.50	SPR	C	N
0.312	7.92	MM-65	.53	13.5	.212	5.4	148	26	.09	2.2	13	58	.25	6.4	0.050	1.3	5.00	SST	CG	N
0.312	7.92	S-27	.53	13.5	.210	5.3	121	21	.11	2.9	14	61	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.312	7.92	S-1016	.56	14.3	.282	7.2	.44	.08	.43	11	.19	.85	.13	3.2	0.015	0.4	7.50	SST	C	N
0.312	7.92	A-24	.56	14.3	.278	7.1	.49	.09	.37	9.3	.18	.80	.20	5.0	0.017	0.4	10.5	SST	C	Z
0.312	7.92	2850	.56	14.3	.272	6.9	4.6	.81	.34	8.5	1.5	6.9	.10	2.5	0.020	0.5	4.00	MW	C	Z
0.312	7.92	YY-41	.56	14.3	.272	6.9	.73	.13	.28	7.2	.21	.92	.28	7.1	0.020	0.5	13.0	SST	C	N
0.312	7.92	10931	.56	14.3	.268	6.8	3.9	.69	.42	11	1.7	7.4	.14	3.6	0.022	0.6	5.50	MW	C	Z
0.312	7.92	3853	.56	14.3	.264	6.7	6.7	1.2	.40	10	2.7	12	.14	3.7	0.024	0.6	5.00	MW	C	Z
0.312	7.92	K-76	.56	14.3	.262	6.7	5.9	1.0	.39	9.8	2.3	10	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.312	7.92	B7-13	.56	14.3	.262	6.7	9.5	1.7	.30	7.6	2.8	13	.11	2.9	0.025	0.6	4.50	MW	CG	N
0.312	7.92	MM-15	.56	14.3	.252	6.4	12	2.0	.37	9.3	4.2	19	.20	5.0	0.030	0.8	6.50	MW	CG	N
0.312	7.92	H-66	.56	14.3	.204	5.2	237	42	.07	1.8	17	77	.27	6.9	0.054	1.4	5.00	SPR	CG	N
0.312	7.92	LL-73	.56	14.3	.192	4.9	258	45	.08	2.2	22	98	.36	9.1	0.060	1.5	6.00	SST	CG	N
0.312	7.92	10509	.59	15.1	.220	5.6	76	13	.15	3.9	12	52	.35	8.8	0.046	1.2	6.50	SPR	C	Z
0.312	7.92	A11-67	.63	15.9	.266	6.8	4.4	.78	.47	12	2.1	9.3	.16	3.9	0.023	0.6	5.75	MW	C	N
0.312	7.92	S-388	.63	15.9	.262	6.7	5.3	.93	.36	9.0	1.9	8.4	.17	4.4	0.025	0.6	5.88	SST	C	N
0.312	7.92	530	.63	15.9	.260	6.6	7.0	1.2	.44	11	3.1	14	.18	4.6	0.026	0.7	6.00	MW	C	Z
0.312	7.92	PP-97	.63	15.9	.258	6.6	9.6	1.7	.25	6.3	2.4	11	.16	4.1	0.027	0.7	5.00	SST	C	N
0.312	7.92	QQ-67	.63	15.9	.256	6.5	11	1.9	.36	9.1	4.0	18	.18	4.6	0.028	0.7	5.50	MW	C	Z
0.312	7.92	Y-20	.63	15.9	.246	6.2	26	4.6	.18	4.5	4.6	21	.20	5.0	0.033	0.8	5.00	SPR	C	N
0.312	7.92	PP-53	.63	15.9	.244	6.2	30	5.2	.17	4.3	5.0	22	.20	5.2	0.034	0.9	5.00	SPR	C	Z
0.312	7.92	FF-85	.63	15.9	.236	6.0	27	4.7	.23	6.0	6.3	28	.26	6.5	0.038	1.0	6.75	SST	CG	N
0.312	7.92	WW-32	.63	15.9	.236	6.0	32	5.5	.20	5.0	6.3	28	.23	5.8	0.038	1.0	6.00	SST	CG	N
0.312	7.92	A14-22	.63	15.9	.230	5.8	41	7.1	.20	5.2	8.3	37	.29	7.3	0.041	1.0	7.00	SPR	CG	GI
0.312	7.92	S-1065	.63	15.9	.204	5.2	124	22	.13	3.3	16	72	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.312	7.92	S-1226	.63	15.9	.188	4.8	278	49	.09	2.2	24	107	.39	9.8	0.062	1.6	6.25	SST	CG	N
0.312	7.92	2846	.66	16.7	.272	6.9	2.3	.40	.52	13	1.2	5.3	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.312	7.92	PP-67	.66	16.7	.272	6.9	2.3	.40	.52	13	1.2	5.3	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.312	7.92	I-42	.66	16.7	.238	6.0	16	2.9	.32	8.2	5.3	24	.33	8.5	0.037	0.9	9.00	SST	CG	N
0.312	7.92	2700	.66	16.7	.230	5.8	45	7.9	.18	4.7	8.3	37	.27	6.8	0.041	1.0	6.50	HD	CG	Z
0.312	7.92	A15-41	.66	16.7	.230	5.8	48	8.5	.16	4.1	7.8	35	.24	6.0	0.041	1.0	5.75	SST	CG	N
0.312	7.92	XX-25	.69	17.4	.256	6.5	7.7	1.4	.46	12	3.6	16	.22	5.7	0.028	0.7	7.00	MW	C	GI
0.312	7.92	4245	.69	17.4	.254	6.5	7.5	1.3	.43											




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.312	7.92	10013	.69	17.5	.236	6.0	24	4.3	.27	7.0	6.7	30	.30	7.7	0.038	1.0	8.00	SPR	CG	Z
0.312	7.92	KK-74	.72	18.2	.240	6.1	15	2.7	.34	8.6	5.2	23	.38	9.6	0.036	0.9	9.50	SPR	C	N
0.312	7.92	4246	.75	19.1	.282	7.2	.35	.06	.59	15	.20	.90	.17	4.2	0.015	0.4	10.0	MW	C	Z
0.312	7.92	S-1072	.75	19.1	.282	7.2	.24	.04	.56	14	.13	.60	.20	5.0	0.015	0.4	12.0	SST	C	N
0.312	7.92	S-23	.75	19.1	.278	7.1	.81	.14	.61	16	.50	2.2	.14	3.5	0.017	0.4	7.00	SST	C	N
0.312	7.92	10422	.75	19.1	.274	7.0	.85	.15	.60	15	.51	2.3	.15	3.7	0.019	0.5	6.75	PB	C	N
0.312	7.92	FF-25	.75	19.1	.272	6.9	.46	.08	.31	7.9	.14	.64	.44	11.2	0.020	0.5	22.0	MW	CG	N
0.312	7.92	B12-32	.75	19.1	.272	6.9	1.5	.27	.57	14	.88	3.9	.18	4.6	0.020	0.5	8.00	MW	C	N
0.312	7.92	S-728	.75	19.1	.268	6.8	3.2	.56	.43	11	1.4	6.1	.15	3.8	0.022	0.6	5.75	SST	C	N
0.312	7.92	WW-44	.75	19.1	.268	6.8	3.5	.60	.60	15	2.1	9.1	.15	3.9	0.022	0.6	6.00	MW	C	N
0.312	7.92	2539	.75	19.1	.266	6.8	3.7	.65	.58	15	2.1	9.5	.17	4.4	0.023	0.6	6.50	MW	C	Z
0.312	7.92	FF-93	.75	19.1	.264	6.7	1.9	.34	.46	12	.89	4.0	.29	7.3	0.024	0.6	11.0	SST	C	N
0.312	7.92	II-29	.75	19.1	.264	6.7	4.0	.70	.56	14	2.2	9.9	.19	4.9	0.024	0.6	7.00	MW	C	Z
0.312	7.92	Z-65	.75	19.1	.262	6.7	4.0	.69	.53	13	2.1	9.2	.23	5.7	0.025	0.6	8.00	MW	C	Z
0.312	7.92	3245	.75	19.1	.258	6.6	6.6	1.2	.53	14	3.5	16	.22	5.5	0.027	0.7	7.00	MW	C	Z
0.312	7.92	3190	.75	19.1	.248	6.3	9.8	1.7	.46	12	4.5	20	.29	7.3	0.032	0.8	9.00	MW	CG	GI
0.312	7.92	946	.75	19.1	.248	6.3	13	2.3	.45	11	5.9	26	.26	6.7	0.032	0.8	7.25	MW	C	Z
0.312	7.92	S-730	.75	19.1	.248	6.3	11	2.0	.35	8.8	3.9	17	.26	6.7	0.032	0.8	7.25	SST	C	N
0.312	7.92	W-17	.75	19.1	.246	6.2	13	2.3	.35	9.0	4.6	21	.30	7.5	0.033	0.8	8.00	SPR	C	N
0.312	7.92	2978	.75	19.1	.244	6.2	9.9	1.7	.38	9.6	3.7	17	.37	9.5	0.034	0.9	11.0	SPR	CG	Z
0.312	7.92	S-146	.75	19.1	.242	6.1	13	2.2	.39	9.9	4.9	22	.35	8.9	0.035	0.9	9.00	SST	C	N
0.312	7.92	S-934	.75	19.1	.242	6.1	14	2.5	.35	8.8	4.9	22	.29	7.3	0.035	0.9	8.25	SST	C	N
0.312	7.92	2585	.75	19.1	.238	6.0	20	3.5	.43	11	8.5	38	.31	8.0	0.037	0.9	8.50	MW	CG	Z
0.312	7.92	B1-5	.75	19.1	.236	6.0	21	3.6	.30	7.7	6.3	28	.31	8.0	0.038	1.0	8.25	SST	CG	N
0.312	7.92	B12-1	.75	19.1	.228	5.8	35	6.1	.26	6.5	8.9	40	.36	9.1	0.042	1.1	8.50	SPR	CG	N
0.312	7.92	O-123	.75	19.1	.220	5.6	57	10	.20	5.2	12	52	.37	9.3	0.046	1.2	8.00	SPR	CG	Z
0.312	7.92	B17-125	.75	19.1	.216	5.5	69	12	.19	4.8	13	59	.38	9.8	0.048	1.2	8.00	SPR	CG	Z
0.312	7.92	O-32	.75	19.1	.210	5.3	137	24	.11	2.7	15	65	.31	7.8	0.051	1.3	6.00	SPR	CG	Z
0.312	7.92	S-204	.78	19.8	.272	6.9	.82	.14	.52	13	.43	1.9	.26	6.6	0.020	0.5	12.0	SST	C	N
0.312	7.92	FF-45	.78	19.8	.252	6.4	8.7	1.5	.54	14	4.7	21	.24	6.1	0.030	0.8	8.00	MW	CG	Z
0.312	7.92	NN-30	.78	19.8	.252	6.4	8.7	1.5	.54	14	4.7	21	.24	6.1	0.030	0.8	8.00	MW	CG	N
0.312	7.92	S-877	.78	19.8	.218	5.5	56	9.8	.21	5.3	12	52	.38	9.6	0.047	1.2	8.00	SST	CG	N
0.312	7.92	BB-62	.78	19.8	.214	5.4	50	8.7	.26	6.7	13	58	.49	12.4	0.049	1.2	10.0	SST	CG	N
0.312	7.92	2617	.78	19.8	.188	4.8	175	31	.15	3.7	26	114	.60	15.4	0.062	1.6	9.75	HD	CG	Z
0.312	7.92	CC-56	.81	20.6	.244	6.2	10	1.8	.45	12	4.7	21	.36	9.1	0.034	0.9	9.50	SST	C	N
0.312	7.92	3678	.81	20.6	.240	6.1	13	2.2	.42	11	5.3	24	.40	10.1	0.036	0.9	11.0	SPR	CG	Z
0.312	7.92	VV-35	.81	20.6	.240	6.1	16	2.9	.35	8.8	5.7	25	.32	8.2	0.036	0.9	9.00	SPR	CG	N
0.312	7.92	LL-52	.81	20.6	.222	5.6	56	9.9	.19	4.9	11	49	.34	8.6	0.045	1.1	7.50	SPR	CG	N
0.312	7.92	S-476	.84	21.4	.244	6.2	9.7	1.7	.47	12	4.6	20	.37	9.5	0.034	0.9	10.0	SST	C	N
0.312	7.92	MM-38	.84	21.4	.232	5.9	18	3.2	.36	9.2	6.6	30	.48	12.2	0.040	1.0	12.0	SPR	CG	Z
0.312	7.92	2614	.84	21.4	.208	5.3	89	16	.24	6.2	22	96	.46	11.6	0.052	1.3	8.75	MW	CG	Z
0.312	7.92	2949	.88	22.2	.272	6.9	1.8	.32	.72	18	1.3	5.9	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.312	7.92	J-81	.88	22.2	.272	6.9	.80	.14	.62	16	.49	2.2	.26	6.6	0.020	0.5	12.0	SST	C	N
0.312	7.92	M-89	.88	22.2	.272	6.9	1.9	.34	.72	18	1.4	6.2	.16	3.9	0.020	0.5	6.75	MW	C	N
0.312	7.92	Q-43	.88	22.2	.272	6.9	1.3	.23	.70	18	.93	4.1	.18	4.6	0.020	0.5	8.00	SST	C	N
0.312	7.92	EE-37	.88	22.2	.272	6.9	1.3	.23	.68	17	.89	4.0	.20	5.1	0.020	0.5	9.00	MW	C	N
0.312	7.92	10544	.88	22.2	.270	6.9	1.4	.25	.64	16	.91	4.1	.23	5.9	0.021	0.5	10.0	MW	C	Z
0.312	7.92	S-729	.88	22.2	.268	6.8	2.7	.47	.51	13	1.4	6.1	.17	4.2	0.022	0.6	6.50	SST	C	N
0.312	7.92	II-17	.88	22.2	.252	6.4	8.7	1.5	.56	14	4.8	22	.24	6.1	0.030	0.8	8.00	MW	CG	N
0.312	7.92	S-731	.88	22.2	.248	6.3	9.6	1.7	.41	10	3.9	17	.30	7.5	0.032	0.8	8.25	SST	C	N
0.312	7.92	W-71	.88	22.2	.188	4.8	161	28	.15	3.8	24	107	.59	15.0	0.062	1.6	9.50	SST	CG	N
0.312	7.92	S-244	.91	23.0	.276	7.0	.69	.12	.72	18	.49	2.2	.19	4.8	0.018	0.5	9.50	SST	C	N
0.312	7.92	3735	.91	23.0	.230	5.8	26	4.5	.33	8.3	8.3	37	.41	10.4	0.041	1.0	10.0	SPR	CG	Z
0.312	7.92	S-231	.91	23.0	.222	5.6	32	5.5	.32	8.2	10	46	.47	12.0	0.045	1.1	10.5	SST	CG	N
0.312	7.92	S-1587	.91	23.0	.222	5.6	33	5.8	.31	7.8	10	46	.46	11.7	0.045	1.1	10.3	SST	CG	N
0.312	7.92	N-138	.91	23.0	.214	5.4	51	8.9	.28	7.0	14	62	.59	14.9	0.049	1.2	11.0	SPR	C	N
0.312	7.92	H-63	.94	23.8	.278	7.1	.46	.08	.71	18	.33	1.5	.22	5.7	0.017	0.4	12.0	MW	C	Z
0.312	7.92	U-12	.94	23.8	.278	7.1	.68	.12	.79	20	.53	2.4	.15	3.9	0.017	0.4	8.00	SST	C	N
0.312	7.92	B1-23	.94	23.8	.260	6.6	4.3	.76	.49	12	2.1	9.5	.20	5.1	0.026	0.7	7.75	SST	CG	N
0.312	7.92	S-394	.94	23.8	.248	6.3	10	1.7	.39	10	3.9	17	.29	7.3	0.032	0.8	8.00	SST	C	N
0.312	7.92	W-98	.94	23.8	.238	6.0	12	2.1	.48	12	5.8	26	.46	11.7	0.037	0.9	11.5	SST	C	N
0.312	7.92	1651	.94	23.8	.230	5.8	16	2.9	.30	7.7	4.9	22	.64	16.2	0.041	1.0	14.5	SPR	C	Z
0.312	7.92	GG-34	.94	23.8	.204	5.2	88	15	.18	4.7	16	72	.49	12.3	0.054	1.4	9.00	SST	CG	N
0.312	7.92	GG-62	.97	24.6	.218	5.5	37	6.6	.31	7.9	12	52	.51	12.8	0.047	1.2	10.8	SST	CG	N
0.312	7.92	CC-2	1.00	25.4	.284	7.2	.35	.06	.87	22	.30	1.4	.13	3.2	0.014	0.4	8.00	MW	C	N
0.312	7.92	B17-126	1.00	25.4	.284	7.2	.38	.07	.88	22	.33	1.5	.12	3.0	0.014	0.4	7.50	MW	C	N
0.312	7.92	202-A	1.00	25.4	.280	7.1	.97	.17	.82	21	.80	3.5	.11	2.7	0.016	0.4	5.75	MW	C	Z
0.312	7.92	W-93	1.00	25.4	.278	7.1	.67	.12	.83	21	.55	2.5	.17	4.3	0.017	0.4	9.00	MW	C	Z
0.312	7.92	10917	1.00	25.4	.272	6.9	1.6	.27	.66	17	1.0	4.6	.17	4.2	0.020	0.5	7.25	SST	C	N
0.312	7.9																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.312	7.92	S-790	1.03	26.2	.232	5.9	15	2.6	.49	13	7.3	32	.52	13.2	0.040	1.0	13.0	SST	CG	N
0.312	7.92	Z-51	1.03	26.2	.186	4.7	244	43	.11	2.8	27	119	.57	14.4	0.063	1.6	8.00	SPR	C	N
0.312	7.92	GG-12	1.06	27.0	.284	7.2	.35	.06	.94	24	.33	1.4	.13	3.2	0.014	0.4	8.00	MW	C	N
0.312	7.92	S-996	1.06	27.0	.276	7.0	.43	.08	.79	20	.34	1.5	.27	6.9	0.018	0.5	14.0	SST	C	N
0.312	7.92	AA-10	1.06	27.0	.272	6.9	.40	.07	.60	15	.24	1.1	.46	11.7	0.020	0.5	22.0	SST	C	N
0.312	7.92	A9-67	1.06	27.0	.254	6.5	6.4	1.1	.68	17	4.4	20	.29	7.4	0.029	0.7	9.00	MW	C	Z
0.312	7.92	3296	1.06	27.0	.252	6.4	6.9	1.2	.70	18	4.8	22	.32	8.0	0.030	0.8	9.50	MW	C	Z
0.312	7.92	V-62	1.06	27.0	.246	6.2	8.0	1.4	.54	14	4.3	19	.35	8.8	0.033	0.8	10.5	SST	CG	N
0.312	7.92	3092	1.06	27.0	.208	5.3	85	15	.18	4.6	15	69	.47	11.9	0.052	1.3	9.00	SPR	CG	Z
0.312	7.92	W-57	1.06	27.0	.204	5.2	56	9.9	.29	7.3	16	72	.70	17.8	0.054	1.4	13.0	SST	CG	N
0.312	7.92	11162	1.13	28.6	.274	7.0	.96	.17	.92	23	.88	3.9	.20	5.2	0.019	0.5	9.75	MW	C	Z
0.312	7.92	10910	1.13	28.6	.272	6.9	.99	.17	.90	23	.89	4.0	.23	5.7	0.020	0.5	10.3	SST	C	N
0.312	7.92	2791	1.13	28.6	.272	6.9	1.3	.23	.93	23	1.2	5.4	.20	5.1	0.020	0.5	9.00	MW	C	GI
0.312	7.92	CC-33	1.13	28.6	.272	6.9	1.5	.27	.97	25	1.5	6.6	.16	4.1	0.020	0.5	8.00	MW	CG	Z
0.312	7.92	S-483	1.13	28.6	.262	6.7	2.1	.36	.80	20	1.7	7.3	.33	8.3	0.025	0.6	12.0	SST	C	N
0.312	7.92	A9-41	1.13	28.6	.258	6.6	4.1	.72	.83	21	3.4	15	.30	7.5	0.027	0.7	10.0	MW	C	N
0.312	7.92	3514	1.13	28.6	.256	6.5	3.4	.59	.72	18	2.4	11	.41	10.3	0.028	0.7	13.5	MW	C	Z
0.312	7.92	3746	1.13	28.6	.252	6.4	6.9	1.2	.70	18	4.8	22	.32	8.0	0.030	0.8	9.50	MW	C	Z
0.312	7.92	HH-97	1.13	28.6	.246	6.2	8.0	1.4	.54	14	4.3	19	.38	9.6	0.033	0.8	10.5	SST	C	N
0.312	7.92	S-791	1.13	28.6	.242	6.1	7.4	1.3	.64	16	4.7	21	.49	12.4	0.035	0.9	14.0	SST	CG	N
0.312	7.92	10147	1.13	28.6	.236	6.0	13	2.3	.50	13	6.7	30	.49	12.5	0.038	1.0	13.0	SPR	CG	Z
0.312	7.92	S-788	1.13	28.6	.204	5.2	58	10	.28	7.1	16	72	.70	17.7	0.054	1.4	12.0	SST	CG	N
0.312	7.92	S-36	1.13	28.6	.186	4.7	104	18	.21	5.4	22	98	.91	23.2	0.063	1.6	14.5	SST	CG	N
0.312	7.92	S-1182	1.16	29.4	.262	6.7	3.4	.60	.55	14	1.9	8.4	.23	5.7	0.025	0.6	8.00	SST	C	N
0.312	7.92	K-43	1.19	30.2	.238	6.0	8.8	1.5	.61	16	5.4	24	.57	14.6	0.037	0.9	15.5	SST	C	N
0.312	7.92	10732	1.19	30.2	.230	5.8	29	5.1	.29	7.3	8.3	37	.37	9.4	0.041	1.0	9.00	SPR	CG	Z
0.312	7.92	B-49	1.19	30.2	.222	5.6	25	4.3	.44	11	11	49	.65	16.6	0.045	1.1	14.5	SPR	CG	Z
0.312	7.92	L-95	1.19	30.2	.168	4.3	279	49	.13	3.3	37	164	.86	21.9	0.072	1.8	12.0	HD	CG	Z
0.312	7.92	S-1686	1.20	30.5	.228	5.8	25	4.3	.34	8.6	8.4	37	.42	10.7	0.042	1.1	10.0	SST	CG	N
0.312	7.92	2807	1.22	31.0	.260	6.6	2.9	.50	.91	23	2.6	12	.31	7.8	0.026	0.7	11.8	MW	CG	Z
0.312	7.92	10504	1.22	31.0	.196	5.0	110	19	.19	4.9	21	94	.70	17.7	0.058	1.5	11.0	SPR	C	Z
0.312	7.92	1859	1.22	31.0	.194	4.9	134	24	.23	5.8	31	137	.65	16.5	0.059	1.5	10.0	MW	C	Z
0.312	7.92	N-38	1.25	31.8	.274	7.0	.81	.14	1.0	26	.84	3.7	.21	5.3	0.019	0.5	10.0	SST	C	N
0.312	7.92	11368	1.25	31.8	.272	6.9	.91	.16	1.0	26	.92	4.1	.24	6.1	0.020	0.5	11.0	SST	C	N
0.312	7.92	10049	1.25	31.8	.264	6.7	2.9	.50	.93	24	2.7	12	.24	6.1	0.024	0.6	9.00	MW	C	GI
0.312	7.92	S-3114	1.25	31.8	.262	6.7	3.4	.60	.55	14	1.9	8.4	.23	5.7	0.025	0.6	8.00	SST	C	N
0.312	7.92	G-3	1.25	31.8	.260	6.6	2.2	.38	.83	21	1.8	8.0	.42	10.6	0.026	0.7	15.0	MW	C	Z
0.312	7.92	AA-84	1.25	31.8	.252	6.4	4.3	.76	.80	20	3.5	15	.45	11.4	0.030	0.8	14.0	MW	C	Z
0.312	7.92	A9-46	1.25	31.8	.250	6.4	4.6	.81	.78	20	3.6	16	.42	10.6	0.031	0.8	13.5	SST	CG	N
0.312	7.92	3715	1.25	31.8	.246	6.2	6.0	1.0	.75	19	4.5	20	.50	12.7	0.033	0.8	15.0	SPR	CG	Z
0.312	7.92	2	1.25	31.8	.230	5.8	17	3.0	.49	12	8.3	37	.62	15.6	0.041	1.0	14.0	HD	C	Z
0.312	7.92	S-495	1.25	31.8	.230	5.8	11	2.0	.53	13	6.0	26	.72	18.4	0.041	1.0	17.7	SST	CG	N
0.312	7.92	S-734	1.25	31.8	.228	5.8	18	3.1	.48	12	8.4	37	.60	15.2	0.042	1.1	13.3	SST	C	N
0.312	7.92	3615	1.25	31.8	.218	5.5	25	4.4	.45	11	11	50	.80	20.3	0.047	1.2	17.0	HD	CG	Z
0.312	7.92	S-3131	1.25	31.8	.210	5.3	39	6.8	.36	9.0	14	61	.73	18.5	0.051	1.3	14.3	SST	CG	N
0.312	7.92	1543	1.25	31.8	.198	5.0	114	20	.18	4.5	20	90	.63	15.9	0.057	1.4	10.0	SPR	C	Z
0.312	7.92	10294	1.31	33.3	.258	6.6	3.0	.53	.93	24	2.8	12	.38	9.6	0.027	0.7	13.0	MW	C	Z
0.312	7.92	10021	1.31	33.3	.256	6.5	3.5	.61	.92	23	3.2	14	.39	10.0	0.028	0.7	13.0	MW	C	Z
0.312	7.92	1857	1.31	33.3	.252	6.4	3.8	.67	.82	21	3.1	14	.50	12.6	0.030	0.8	15.5	MW	C	Z
0.312	7.92	10328	1.31	33.3	.250	6.4	3.6	.63	.71	18	2.6	11	.61	15.4	0.031	0.8	18.5	MW	C	Z
0.312	7.92	3533	1.31	33.3	.250	6.4	5.1	.89	.85	22	4.4	19	.46	11.6	0.031	0.8	13.8	MW	C	Z
0.312	7.92	10193	1.31	33.3	.248	6.3	4.9	.86	.80	20	3.9	17	.51	13.0	0.032	0.8	16.0	SPR	CG	Z
0.312	7.92	10024	1.31	33.3	.246	6.2	6.5	1.1	.71	18	4.6	21	.50	12.6	0.033	0.8	14.0	SPR	C	Z
0.312	7.92	NN-78	1.31	33.3	.218	5.5	25	4.4	.49	13	12	55	.80	20.3	0.047	1.2	17.0	SPR	CG	N
0.312	7.92	L-59	1.31	33.3	.208	5.3	40	7.0	.36	9.3	15	65	.78	19.8	0.052	1.3	15.0	SST	CG	N
0.312	7.92	NN-79	1.31	33.3	.192	4.9	93	16	.25	6.4	23	104	.93	23.6	0.060	1.5	14.5	SPR	C	N
0.312	7.92	1697	1.31	33.3	.190	4.8	180	31	.14	3.4	24	109	.61	15.5	0.061	1.5	9.00	SPR	C	Z
0.312	7.92	B11-19	1.34	34.1	.274	7.0	.57	.10	1.1	27	.61	2.7	.29	7.2	0.019	0.5	15.0	MW		




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F.N.D.S	F.W.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.312	7.92	6	1.50	38.1	.244	6.2	6.7	1.2	.75	19	5.0	22	.55	14.0	0.034	0.9	15.3	HD	C	Z
0.312	7.92	K-23	1.50	38.1	.242	6.1	6.5	1.1	.75	19	4.9	22	.58	14.7	0.035	0.9	15.5	SST	C	N
0.312	7.92	3908	1.50	38.1	.228	5.8	17	3.1	.51	13	8.9	40	.67	17.1	0.042	1.1	15.0	SPR	C	Z
0.312	7.92	S-735	1.50	38.1	.228	5.8	14	2.5	.58	15	8.4	37	.70	17.9	0.042	1.1	15.8	SST	C	N
0.312	7.92	N-70	1.50	38.1	.222	5.6	27	4.7	.41	10	11	49	.61	15.4	0.045	1.1	13.5	SPR	CG	GI
0.312	7.92	B14-31	1.50	38.1	.220	5.6	26	4.6	.44	11	12	52	.74	18.7	0.046	1.2	15.0	SPR	C	Z
0.312	7.92	936	1.50	38.1	.218	5.5	29	5.1	.43	11	12	55	.75	19.1	0.047	1.2	15.0	HD	C	Z
0.312	7.92	11237	1.50	38.1	.208	5.3	37	6.5	.41	11	15	69	.99	25.1	0.052	1.3	18.0	SPR	C	Z
0.312	7.92	11383	1.50	38.1	.198	5.0	87	15	.23	5.9	20	90	.71	18.1	0.057	1.4	12.5	HD	CG	Z
0.312	7.92	2823	1.53	38.9	.240	6.1	8.5	1.5	.93	24	7.9	35	.56	14.2	0.036	0.9	15.5	MW	CG	Z
0.312	7.92	S-180	1.59	40.5	.264	6.7	1.4	.24	1.2	31	1.7	7.5	.36	9.1	0.024	0.6	15.0	SST	CG	N
0.312	7.92	PP-65	1.63	41.3	.272	6.9	.92	.16	1.4	35	1.3	5.7	.24	6.1	0.020	0.5	12.0	MW	CG	Z
0.312	7.92	J-100	1.63	41.3	.242	6.1	6.3	1.1	.78	20	4.9	22	.56	14.2	0.035	0.9	16.0	SST	CG	N
0.312	7.92	WW-59	1.63	41.3	.242	6.1	6.3	1.1	.83	21	5.2	23	.63	16.0	0.035	0.9	18.0	SPR	CG	N
0.312	7.92	116	1.63	41.3	.230	5.8	13	2.2	.65	17	8.3	37	.78	19.8	0.041	1.0	18.0	HD	C	Z
0.312	7.92	10127	1.63	41.3	.228	5.8	17	3.1	.51	13	8.9	40	.67	17.1	0.042	1.1	15.0	SPR	C	Z
0.312	7.92	10916	1.63	41.3	.208	5.3	37	6.4	.42	11	15	69	1.00	25.4	0.052	1.3	18.3	SPR	C	N
0.312	7.92	10535	1.63	41.3	.202	5.1	48	8.5	.38	9.5	18	81	1.05	26.5	0.055	1.4	18.0	SPR	C	Z
0.312	7.92	A15-38	1.66	42.1	.256	6.5	1.6	.29	1.0	26	1.7	7.5	.64	16.2	0.028	0.7	22.8	SST	CG	N
0.312	7.92	12432	1.72	43.6	.250	6.4	5.3	.93	1.0	26	5.3	24	.44	11.2	0.031	0.8	13.3	MW	C	Z
0.312	7.92	202-C	1.75	44.5	.280	7.1	.39	.07	1.6	39	.61	2.7	.20	5.0	0.016	0.4	11.3	MW	C	Z
0.312	7.92	FF-42	1.75	44.5	.272	6.9	.97	.17	1.5	38	1.5	6.5	.25	6.4	0.020	0.5	11.5	MW	C	Z
0.312	7.92	4196	1.75	44.5	.260	6.6	2.8	.49	1.1	29	3.2	14	.34	8.6	0.026	0.7	12.0	MW	C	Z
0.312	7.92	JJ-100	1.75	44.5	.232	5.9	7.6	1.3	.79	20	6.0	27	.96	24.4	0.040	1.0	23.0	SST	C	N
0.312	7.92	10100	1.75	44.5	.222	5.6	23	4.0	.48	12	11	49	.74	18.9	0.045	1.1	15.5	SPR	C	Z
0.312	7.92	HH-93	1.75	44.5	.212	5.4	29	5.1	.47	12	14	62	.95	24.1	0.050	1.3	19.0	SPR	CG	N
0.312	7.92	3395	1.75	44.5	.198	5.0	48	8.4	.42	11	20	90	1.20	30.4	0.057	1.4	21.0	SPR	CG	Z
0.312	7.92	1937	1.75	44.5	.196	5.0	78	14	.27	6.9	21	94	.91	23.2	0.058	1.5	14.8	SPR	C	Z
0.312	7.92	B15-25	1.75	44.5	.180	4.6	126	22	.24	6.1	30	136	1.16	29.3	0.066	1.7	16.5	SPR	C	N
0.312	7.92	3183	1.78	45.2	.248	6.3	6.1	1.1	.97	25	5.9	26	.46	11.6	0.032	0.8	13.3	MW	C	Z
0.312	7.92	00-87	1.88	47.6	.242	6.1	5.1	.89	1.0	26	5.2	23	.81	20.4	0.035	0.9	22.0	SPR	C	Z
0.312	7.92	10481	1.88	47.6	.230	5.8	11	2.0	.74	19	8.3	37	.86	21.9	0.041	1.0	20.0	SPR	C	Z
0.312	7.92	U-54	1.94	49.2	.260	6.6	2.0	.35	1.5	39	3.1	14	.42	10.6	0.026	0.7	16.0	MW	C	N
0.312	7.92	1942	1.94	49.2	.232	5.9	10	1.8	.75	19	7.8	35	.83	21.1	0.040	1.0	19.8	SPR	C	Z
0.312	7.92	J-87	1.94	49.2	.232	5.9	9.9	1.7	.73	19	7.3	32	.72	18.3	0.040	1.0	18.0	SST	CG	N
0.312	7.92	S-910	2.00	50.8	.264	6.7	1.4	.25	1.2	31	1.8	7.9	.34	8.5	0.024	0.6	14.0	SST	CG	N
0.312	7.92	9	2.00	50.8	.218	5.5	18	3.1	.70	18	12	55	1.14	28.9	0.047	1.2	23.3	HD	C	Z
0.312	7.92	S-297	2.00	50.8	.218	5.5	20	3.5	.58	15	12	52	.90	23.0	0.047	1.2	18.3	SST	C	N
0.312	7.92	3128	2.00	50.8	.214	5.4	28	5.0	.49	12	14	62	.93	23.6	0.049	1.2	18.0	SPR	C	Z
0.312	7.92	937	2.00	50.8	.204	5.2	44	7.8	.39	9.9	17	77	1.03	26.1	0.054	1.4	18.0	HD	C	Z
0.312	7.92	4122	2.13	54.0	.232	5.9	10	1.8	.76	19	7.8	35	.84	21.3	0.040	1.0	20.0	SPR	C	Z
0.312	7.92	S-821	2.16	54.8	.240	6.1	4.1	.71	1.2	30	4.8	21	.99	25.1	0.036	0.9	26.5	SST	C	N
0.312	7.92	S-1030	2.25	57.2	.228	5.8	9.9	1.7	.85	22	8.4	37	.92	23.5	0.042	1.1	22.0	SST	CG	N
0.312	7.92	Z-61	2.25	57.2	.228	5.8	13	2.3	.69	17	8.9	40	.82	20.8	0.042	1.1	19.5	SPR	CG	GI
0.312	7.92	12262	2.31	58.7	.256	6.5	1.9	.34	1.7	42	3.2	14	.64	16.4	0.028	0.7	22.0	MW	C	Z
0.312	7.92	12196	2.34	59.5	.216	5.5	22	3.8	.60	15	13	59	1.01	25.6	0.048	1.2	21.0	SPR	CG	Z
0.312	7.92	G-28	2.38	60.3	.218	5.5	17	2.9	.69	18	12	52	1.03	26.3	0.047	1.2	22.0	SST	CG	N
0.312	7.92	A9-62	2.50	63.5	.250	6.4	3.0	.52	1.8	45	5.3	24	.71	18.1	0.031	0.8	22.0	MW	C	Z
0.312	7.92	F-58	2.50	63.5	.208	5.3	24	4.2	.65	16	15	69	1.40	35.7	0.052	1.3	27.0	SPR	CG	GI
0.312	7.92	S-218	2.75	69.9	.260	6.6	.86	.15	1.9	49	1.7	7.4	.81	20.6	0.026	0.7	30.3	SST	C	N
0.312	7.92	B9-58	2.75	69.9	.202	5.1	36	6.2	.51	13	18	81	1.31	33.2	0.055	1.4	23.8	SPR	CG	N
0.312	7.92	S-1684	2.88	73.0	.274	7.0	.23	.04	2.3	58	.52	2.3	.60	15.2	0.019	0.5	30.5	SST	C	N
0.312	7.92	KK-11	3.00	76.2	.252	6.4	1.7	.30	1.9	48	3.2	14	.90	22.9	0.030	0.8	29.0	SST	C	N
0.312	7.92	Y-13	3.00	76.2	.248	6.3	2.3	.40	1.7	44	3.9	17	.94	23.8	0.032	0.8	28.3	SST	C	N
0.312	7.92	M-115	3.13	79.4	.216	5.5	12	2.1	1.1	28	13	59	1.78	45.1	0.048	1.2	37.0	SPR	CG	N
0.312	7.92	F-57	3.25	82.6	.224	5.7	8.5	1.5	1.2	31	10	46	1.54	39.1	0.044	1.1	35.0	HD	CG	Z
0.312	7.92	4109	3.25	82.6	.220	5.6	13	2.3	.87	22	12	52	1.31	33.3	0.046	1.2	27.5	SPR	C	N
0.312	7.92	1573	3.38	85.7	.242	6.1	4.2	.73	1.3	32	5.2	23	.95	24.2	0.035	0.9	26.3	SPR	C	Z
0.312	7.92	12498	3.																	



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.328	8.33	H-58	.34	8.7	.296	7.5	.92	.16	.25	6.3	.23	1.0	.10	2.4	0.016	0.4	5.00	SST	C	N
0.328	8.33	EE-32	.38	9.5	.270	6.9	8.3	1.4	.20	5.1	1.7	7.4	.17	4.4	0.029	0.7	6.00	SST	CG	N
0.328	8.33	XX-44	.38	9.5	.264	6.7	29	5.1	.14	3.5	4.0	18	.16	4.1	0.032	0.8	4.00	HD	C	Z
0.328	8.33	MM-69	.38	9.7	.208	5.3	429	75	.05	1.2	21	94	.30	7.6	0.060	1.5	4.00	SST	C	N
0.328	8.33	S-4	.41	10.3	.280	7.1	4.9	.86	.26	6.7	1.3	5.7	.14	3.7	0.024	0.6	5.00	SST	C	N
0.328	8.33	I-38	.44	11.1	.276	7.0	12	2.1	.25	6.5	3.0	13	.10	2.6	0.026	0.7	4.00	MW	CG	GI
0.328	8.33	II-31	.44	11.1	.268	6.8	22	3.9	.21	5.3	4.6	21	.12	3.0	0.030	0.8	4.00	MW	CG	Z
0.328	8.33	KK-1	.44	11.1	.268	6.8	5.5	.96	.14	3.5	.76	3.4	.30	7.6	0.030	0.8	10.0	MW	CG	Z
0.328	8.33	GG-24	.44	11.1	.258	6.6	25	4.4	.18	4.7	4.7	21	.18	4.4	0.035	0.9	5.00	SST	CG	N
0.328	8.33	2944	.44	11.1	.256	6.5	52	9.1	.11	2.7	5.4	24	.18	4.5	0.036	0.9	4.00	SPR	C	Z
0.328	8.33	A10-27	.44	11.1	.256	6.5	34	6.0	.15	3.8	5.1	23	.16	4.1	0.036	0.9	4.50	SST	CG	N
0.328	8.33	S-817	.44	11.1	.252	6.4	27	4.7	.21	5.3	5.6	25	.23	5.8	0.038	1.0	6.00	SST	CG	N
0.328	8.33	VV-43	.44	11.1	.246	6.2	40	7.0	.19	4.8	7.5	33	.24	6.0	0.041	1.0	5.75	SST	CG	N
0.328	8.33	3669	.44	11.1	.244	6.2	64	11	.13	3.4	8.5	38	.21	5.3	0.042	1.1	5.00	SPR	CG	Z
0.328	8.33	Y-71	.44	11.1	.238	6.0	116	20	.09	2.3	10	46	.19	4.9	0.045	1.1	4.25	SPR	CG	N
0.328	8.33	O-117	.50	12.7	.264	6.7	12	2.0	.24	6.2	2.8	13	.26	6.5	0.032	0.8	7.00	SPR	C	GI
0.328	8.33	2578	.50	12.7	.262	6.7	17	2.9	.27	6.7	4.4	20	.23	5.9	0.033	0.8	6.00	HD	C	Z
0.328	8.33	W-86	.50	12.7	.238	6.0	57	9.9	.17	4.4	9.8	44	.27	6.9	0.045	1.1	6.00	SST	CG	N
0.328	8.33	A10-51	.50	12.7	.236	6.0	31	5.5	.18	4.5	5.6	25	.32	8.2	0.046	1.2	7.00	SPR	CG	N
0.328	8.33	B4-11	.50	12.7	.236	6.0	72	13	.16	3.9	11	50	.28	7.0	0.046	1.2	6.00	SPR	CG	Z
0.328	8.33	3717	.50	12.7	.192	4.9	437	77	.07	1.8	32	142	.41	10.4	0.068	1.7	6.00	SPR	CG	Z
0.328	8.33	J-76	.50	12.7	.184	4.7	768	134	.05	1.2	35	158	.36	9.1	0.072	1.8	5.00	SPR	CG	N
0.328	8.33	2673	.56	14.3	.264	6.7	27	4.8	.21	5.2	5.6	25	.13	3.4	0.032	0.8	4.00	MW	CG	GI
0.328	8.33	11132	.56	14.3	.238	6.0	61	11	.17	4.3	10	46	.33	8.3	0.045	1.1	6.25	SPR	C	Z
0.328	8.33	I-11	.56	14.3	.226	5.7	101	18	.13	3.3	13	59	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.328	8.33	O-1	.59	15.1	.302	7.7	.19	.03	.46	12	.09	.39	.13	3.3	0.013	0.3	9.00	MW	C	GI
0.328	8.33	2671	.59	15.1	.288	7.3	3.9	.69	.37	9.5	1.5	6.6	.10	2.5	0.020	0.5	4.00	MW	C	Z
0.328	8.33	CC-97	.59	15.1	.242	6.1	42	7.4	.22	5.5	9.1	41	.30	7.6	0.043	1.1	7.00	SPR	CG	Z
0.328	8.33	A-17	.63	15.9	.300	7.6	.25	.04	.49	12	.12	.55	.14	3.6	0.014	0.4	9.00	MW	C	Z
0.328	8.33	BB-97	.63	15.9	.278	7.1	4.0	.71	.43	11	1.7	7.6	.20	5.1	0.025	0.6	7.00	MW	C	Z
0.328	8.33	L-36	.63	15.9	.278	7.1	4.5	.79	.46	12	2.1	9.2	.16	4.1	0.025	0.6	6.50	MW	CG	N
0.328	8.33	S-1429	.63	15.9	.270	6.9	8.3	1.4	.34	8.6	2.8	12	.20	5.2	0.029	0.7	6.00	SST	C	N
0.328	8.33	W-65	.63	15.9	.264	6.7	15	2.5	.28	7.0	4.0	18	.22	5.7	0.032	0.8	6.00	SPR	C	Z
0.328	8.33	FF-47	.63	15.9	.258	6.6	19	3.3	.25	6.4	4.7	21	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.328	8.33	S-797	.63	15.9	.258	6.6	15	2.6	.31	8.0	4.7	21	.25	6.2	0.035	0.9	7.00	SST	CG	N
0.328	8.33	A13-45	.63	15.9	.242	6.1	35	6.2	.26	6.6	9.1	41	.34	8.7	0.043	1.1	8.00	SPR	CG	N
0.328	8.33	LL-94	.63	15.9	.204	5.2	245	43	.09	2.4	23	103	.37	9.4	0.062	1.6	6.00	SST	CG	N
0.328	8.33	B3-44	.66	16.7	.282	7.2	2.4	.41	.45	11	1.1	4.7	.21	5.3	0.023	0.6	8.00	MW	C	Z
0.328	8.33	O-142	.66	16.7	.246	6.2	30	5.3	.24	6.2	7.5	33	.29	7.3	0.041	1.0	7.00	SST	CG	N
0.328	8.33	Z-92	.66	16.7	.244	6.2	55	9.6	.16	4.0	8.5	38	.27	6.9	0.042	1.1	5.50	SPR	C	Z
0.328	8.33	I-76	.66	16.7	.236	6.0	51	8.9	.20	5.2	10	46	.32	8.2	0.046	1.2	7.00	SST	CG	N
0.328	8.33	B15-56	.69	17.4	.302	7.7	.19	.03	.57	14	.11	.49	.12	3.0	0.013	0.3	8.00	SST	C	N
0.328	8.33	S-893	.69	17.4	.274	7.0	6.6	1.2	.34	8.7	2.3	10	.18	4.6	0.027	0.7	5.75	SST	C	N
0.328	8.33	CC-77	.69	17.4	.272	6.9	6.9	1.2	.50	13	3.4	15	.19	4.8	0.028	0.7	6.75	MW	CG	N
0.328	8.33	A12-32	.69	17.4	.262	6.7	14	2.5	.28	7.2	4.1	18	.23	5.9	0.033	0.8	6.00	SST	C	N
0.328	8.33	S-3143	.69	17.4	.246	6.2	40	7.0	.19	4.8	7.5	33	.28	7.0	0.041	1.0	5.75	SST	C	N
0.328	8.33	U-40	.69	17.4	.234	5.9	53	9.2	.22	5.7	12	53	.38	9.6	0.047	1.2	8.00	SPR	CG	Z
0.328	8.33	A9-43	.72	18.2	.278	7.1	4.5	.78	.40	10	1.8	8.0	.18	4.4	0.025	0.6	6.00	SST	C	N
0.328	8.33	2872	.72	18.2	.270	6.9	5.9	1.0	.44	11	2.6	12	.28	7.0	0.029	0.7	8.50	MW	C	Z
0.328	8.33	12500	.72	18.3	.228	5.8	73	13	.18	4.6	13	59	.44	11.1	0.050	1.3	7.75	SPR	C	N
0.328	8.33	MM-17	.75	19.1	.300	7.6	.20	.03	.58	15	.12	.51	.17	4.3	0.014	0.4	11.0	MW	C	Z
0.328	8.33	I-19	.75	19.1	.296	7.5	.56	.10	.61	16	.35	1.5	.14	3.5	0.016	0.4	7.50	MW	C	N
0.328	8.33	S-3000	.75	19.1	.272	6.9	4.7	.83	.50	13	2.4	11	.25	6.4	0.028	0.7	8.00	SST	C	N
0.328	8.33	KK-46	.75	19.1	.268	6.8	9.8	1.7	.32	8.1	3.1	14	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.328	8.33	Y-88	.75	19.1	.268	6.8	5.5	.96	.45	11	2.5	11	.30	7.6	0.030	0.8	9.00	SST	C	N
0.328	8.33	10022	.75	19.1	.266	6.8	6.3	1.1	.41	10	2.6	12	.34	8.7	0.031	0.8	10.0	MW	C	Z
0.328	8.33	2546	.75	19.1	.258	6.6	12	2.1	.40	10	4.9	22	.35	8.9	0.035	0.9	9.00	MW	C	Z
0.328	8.33	A-86	.75	19.1	.248	6.3	26	4.5	.29	7.3	7.4	33	.32	8.1	0.040	1.0	8.00	SPR	CG	Z
0.328	8.33	K-68	.75	19.1	.248	6.3	27	4.7	.26	6.6	6.9	31	.28							




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.328	8.33	HH-38	1.00	25.4	.282	7.2	1.4	.25	.70	18	.99	4.4	.30	7.6	0.023	0.6	12.0	MW	C	N
0.328	8.33	I-9	1.00	25.4	.274	7.0	3.3	.58	.69	18	2.3	10	.31	7.9	0.027	0.7	10.5	MW	C	Z
0.328	8.33	VW-53	1.00	25.4	.254	6.5	14	2.4	.41	10	5.5	25	.33	8.5	0.037	0.9	9.00	SST	CG	N
0.328	8.33	CC-69	1.00	25.4	.248	6.3	19	3.4	.38	9.8	7.4	33	.40	10.2	0.040	1.0	10.0	SPR	CG	Z
0.328	8.33	2581	1.00	25.4	.242	6.1	33	5.7	.39	9.8	13	56	.41	10.4	0.043	1.1	8.50	MW	C	Z
0.328	8.33	10040	1.00	25.4	.238	6.0	37	6.5	.28	7.1	10	46	.45	11.4	0.045	1.1	9.00	SPR	C	Z
0.328	8.33	10536	1.00	25.4	.238	6.0	27	4.8	.38	9.7	10	46	.56	14.3	0.045	1.1	11.5	SPR	C	Z
0.328	8.33	B4-25	1.00	25.4	.238	6.0	33	5.7	.44	11	14	64	.45	11.4	0.045	1.1	10.0	MW	CG	N
0.328	8.33	J-16	1.00	25.4	.224	5.7	71	13	.21	5.3	15	66	.47	11.9	0.052	1.3	9.00	SPR	CG	Z
0.328	8.33	O-103	1.03	26.2	.256	6.5	13	2.3	.42	11	5.4	24	.38	9.6	0.036	0.9	9.50	SPR	C	GI
0.328	8.33	A-69	1.06	27.0	.276	7.0	2.0	.35	.70	18	1.4	6.2	.36	9.2	0.026	0.7	14.0	MW	CG	N
0.328	8.33	Y-96	1.06	27.0	.232	5.9	40	7.0	.32	8.1	13	56	.52	13.1	0.048	1.2	10.8	SPR	CG	N
0.328	8.33	B14-28	1.09	27.8	.290	7.4	.63	.11	.87	22	.55	2.4	.23	5.8	0.019	0.5	12.0	MW	CG	N
0.328	8.33	10255	1.09	27.8	.278	7.1	2.2	.39	.79	20	1.8	7.9	.30	7.6	0.025	0.6	11.0	MW	C	N
0.328	8.33	W-27	1.09	27.8	.220	5.6	59	10	.27	6.7	16	69	.59	15.1	0.054	1.4	11.0	SST	CG	N
0.328	8.33	CC-51	1.13	28.6	.268	6.8	6.8	1.2	.68	17	4.6	21	.29	7.2	0.030	0.8	8.50	MW	C	Z
0.328	8.33	HH-27	1.13	28.6	.268	6.8	4.6	.80	.67	17	3.1	14	.32	8.0	0.030	0.8	10.5	SST	CG	N
0.328	8.33	A-98	1.13	28.6	.256	6.5	11	2.0	.48	12	5.4	24	.38	9.6	0.036	0.9	10.5	HD	CG	N
0.328	8.33	S-229	1.13	28.6	.242	6.1	28	5.0	.30	7.7	8.6	38	.37	9.3	0.043	1.1	8.50	SST	C	N
0.328	8.33	Q-40	1.13	28.6	.238	6.0	18	3.2	.47	12	8.5	38	.65	16.6	0.045	1.1	14.5	SST	CG	N
0.328	8.33	S-413	1.13	28.6	.228	5.8	39	6.8	.32	8.1	12	55	.58	14.6	0.050	1.3	11.5	SST	CG	N
0.328	8.33	00-72	1.13	28.6	.228	5.8	119	21	.11	2.8	13	59	.28	7.0	0.050	1.3	5.50	SPR	CG	Z
0.328	8.33	3606	1.13	28.6	.220	5.6	99	17	.17	4.2	17	74	.49	12.3	0.054	1.4	8.00	HD	C	Z
0.328	8.33	NN-36	1.19	30.2	.268	6.8	6.0	1.1	.52	13	3.1	14	.29	7.2	0.030	0.8	8.50	SST	C	N
0.328	8.33	B7-26	1.19	30.2	.248	6.3	13	2.3	.55	14	7.4	33	.54	13.7	0.040	1.0	13.5	SPR	CG	N
0.328	8.33	11101	1.19	30.2	.234	5.9	40	6.9	.30	7.6	12	53	.47	11.9	0.047	1.2	10.0	SPR	CG	Z
0.328	8.33	3958	1.19	30.2	.226	5.7	46	8.0	.31	7.8	14	62	.61	15.5	0.051	1.3	12.0	SPR	CG	Z
0.328	8.33	1507	1.19	30.2	.204	5.2	150	26	.23	5.7	34	151	.59	15.0	0.062	1.6	9.50	MW	CG	Z
0.328	8.33	I-3	1.22	31.0	.230	5.8	40	7.0	.33	8.5	13	59	.56	14.3	0.049	1.2	11.5	SPR	CG	N
0.328	8.33	PP-34	1.25	31.8	.288	7.3	.70	.12	.99	25	.69	3.1	.26	6.6	0.020	0.5	12.0	SST	C	N
0.328	8.33	3565	1.25	31.8	.272	6.9	4.1	.72	.92	23	3.8	17	.31	7.8	0.028	0.7	10.0	MW	C	Z
0.328	8.33	MM-74	1.25	31.8	.264	6.7	5.3	.93	.70	18	3.7	17	.40	10.2	0.032	0.8	11.5	SST	C	N
0.328	8.33	NN-27	1.25	31.8	.248	6.3	11	2.0	.61	15	6.9	31	.60	15.2	0.040	1.0	14.0	SST	C	N
0.328	8.33	EE-90	1.25	31.8	.188	4.8	251	44	.13	3.3	33	146	.70	17.8	0.070	1.8	10.0	SPR	CG	N
0.328	8.33	HH-2	1.25	31.8	.148	3.8	777	136	.08	2.0	62	276	.99	25.1	0.090	2.3	11.0	SPR	CG	GI
0.328	8.33	10876	1.28	32.5	.288	7.3	.87	.15	1.1	27	.93	4.1	.22	5.6	0.020	0.5	10.0	SST	C	N
0.328	8.33	10576	1.28	32.5	.258	6.6	7.6	1.3	.62	16	4.7	21	.42	10.7	0.035	0.9	12.0	SST	CG	N
0.328	8.33	10720	1.28	32.5	.246	6.2	16	2.7	.51	13	8.0	35	.57	14.6	0.041	1.0	13.0	SPR	C	Z
0.328	8.33	00-97	1.28	32.5	.208	5.3	143	25	.15	3.7	21	94	.54	13.7	0.060	1.5	8.00	SST	C	N
0.328	8.33	2783	1.31	33.3	.266	6.8	7.9	1.4	.64	16	5.1	23	.29	7.4	0.031	0.8	8.25	MW	C	Z
0.328	8.33	S-186	1.31	33.3	.204	5.2	109	19	.21	5.4	23	103	.68	17.3	0.062	1.6	11.0	SST	CG	N
0.328	8.33	3644	1.38	34.9	.296	7.5	.41	.07	1.2	31	.50	2.2	.17	4.3	0.016	0.4	9.50	MW	C	N
0.328	8.33	11452	1.38	34.9	.234	5.9	35	6.2	.34	8.6	12	53	.56	14.3	0.047	1.2	11.0	HD	C	Z
0.328	8.33	1905	1.38	34.9	.146	3.7	823	144	.08	2.0	64	284	1.00	25.4	0.091	2.3	11.0	SPR	CG	Z
0.328	8.33	10534	1.41	35.7	.266	6.8	3.7	.65	.89	23	3.3	15	.52	13.2	0.031	0.8	15.8	MW	C	Z
0.328	8.33	S-825	1.41	35.7	.236	6.0	21	3.6	.50	13	10	46	.64	16.4	0.046	1.2	14.0	SST	CG	N
0.328	8.33	12468	1.47	37.3	.284	7.2	.98	.17	1.2	29	1.1	5.1	.31	7.8	0.022	0.6	14.0	MW	CG	Z
0.328	8.33	KK-59	1.47	37.3	.228	5.8	35	6.1	.38	9.6	13	59	.70	17.8	0.050	1.3	14.0	SPR	CG	N
0.328	8.33	MM-72	1.50	38.1	.288	7.3	.87	.15	1.1	29	.98	4.4	.22	5.6	0.020	0.5	10.0	SST	C	N
0.328	8.33	S-1159	1.50	38.1	.278	7.1	1.8	.32	.98	25	1.8	8.0	.31	7.9	0.025	0.6	11.5	SST	C	N
0.328	8.33	12251	1.50	38.1	.268	6.8	2.7	.47	1.0	26	2.7	12	.50	12.6	0.030	0.8	16.5	SST	CG	N
0.328	8.33	VV-70	1.50	38.1	.266	6.8	3.0	.52	.88	22	2.6	12	.62	15.7	0.031	0.8	19.0	MW	C	Z
0.328	8.33	K-30	1.50	38.1	.252	6.4	8.5	1.5	.70	18	6.0	27	.59	15.0	0.038	1.0	14.5	SST	C	N
0.328	8.33	O-59	1.50	38.1	.250	6.4	8.6	1.5	.80	20	6.9	31	.70	17.8	0.039	1.0	18.0	SPR	CG	Z
0.328	8.33	Q-47	1.59	40.5	.260	6.6	5.0	.88	.96	24	4.8	21	.58	14.7	0.034	0.9	17.0	SPR	CG	N
0.328	8.33	A11-57	1.59	40.5	.256	6.5	14	2.4	.39	10	5.4	24	.36	9.1	0.036	0.9	9.00	SPR	C	Z
0.328	8.33	L-54	1.69	42.8	.234	5.9	21	3.7	.56	14	12	53	.80	20.3	0.047	1.2	17.0	SPR	CG	Z
0.328	8.33	RR-69	1.69	42.8	.184	4.7	149	26	.24	6.1	35	158	1.26	32.0	0.072	1.8	17.5	HD	CG	Z
0.328	8.33	12212	1.75	44.5	.244	6.2	16	2.8	.54	14	8.5	38	.59	14.						



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.328	8.33	1934	3.38	85.7	.254	6.5	4.3	.76	1.4	35	5.9	26	1.05	26.5	0.037	0.9	27.3	SPR	C	Z
0.328	8.33	S-3074	4.13	104.8	.274	7.0	.80	.14	2.8	72	2.3	10	.90	23.0	0.027	0.7	32.5	SST	C	N
0.328	8.33	S-3099	4.25	108.0	.274	7.0	.63	.11	3.1	79	2.0	8.8	1.12	28.5	0.027	0.7	40.5	SST	C	N
0.328	8.33	K-54	4.25	108.0	.258	6.6	2.0	.34	2.4	61	4.7	21	1.44	36.4	0.035	0.9	40.0	SST	C	N
0.338	8.59	12753	1.48	37.7	.274	7.0	5.3	.92	.74	19	3.9	17	.42	10.6	0.032	0.8	12.0	SPR	C	N
0.343	8.71	W-99	.16	4.0	.295	7.5	6.5	1.1	.04	.91	.23	1.0	.12	3.0	0.024	0.6	4.00	SST	C	N
0.343	8.71	S-855	.19	4.8	.285	7.2	46	8.0	.06	1.5	2.7	12	.08	1.9	0.029	0.7	2.50	SST	C	N
0.343	8.71	S-1324	.25	6.4	.273	6.9	32	5.6	.08	1.9	2.4	11	.18	4.4	0.035	0.9	4.00	SST	C	N
0.343	8.71	U-95	.28	7.1	.283	7.2	19	3.3	.16	4.1	3.1	14	.12	3.0	0.030	0.8	4.00	MW	CG	N
0.343	8.71	PP-51	.28	7.1	.243	6.2	211	37	.06	1.4	12	53	.18	4.4	0.050	1.3	3.50	SST	CG	N
0.343	8.71	DD-77	.31	7.9	.315	8.0	.31	.05	.20	5.1	.06	.28	.11	2.8	0.014	0.4	7.00	MW	C	N
0.343	8.71	GG-54	.31	7.9	.295	7.5	9.8	1.7	.20	5.2	2.0	8.9	.11	2.7	0.024	0.6	3.50	MW	C	N
0.343	8.71	U-74	.31	7.9	.283	7.2	8.3	1.4	.10	2.6	.84	3.7	.21	5.3	0.030	0.8	6.00	SST	C	N
0.343	8.71	2731	.31	7.9	.275	7.0	65	11	.07	1.8	4.6	21	.14	3.5	0.034	0.9	3.00	SPR	C	Z
0.343	8.71	B7-25	.34	8.7	.303	7.7	3.9	.68	.27	6.8	1.0	4.6	.08	1.9	0.020	0.5	3.75	MW	CG	N
0.343	8.71	G-52	.34	8.7	.261	6.6	49	8.6	.14	3.5	6.8	30	.21	5.2	0.041	1.0	5.00	SPR	CG	Z
0.343	8.71	B-71	.38	9.5	.315	8.0	.52	.09	.29	7.4	.15	.67	.08	2.1	0.014	0.4	5.00	MW	C	Z
0.343	8.71	O-53	.38	9.5	.293	7.4	7.6	1.3	.23	5.8	1.7	7.7	.13	3.2	0.025	0.6	4.00	SST	C	N
0.343	8.71	NN-40	.38	9.5	.283	7.2	19	3.3	.23	5.7	4.3	19	.15	3.8	0.030	0.8	4.00	MW	C	Z
0.343	8.71	B14-33	.38	9.5	.277	7.0	13	2.4	.17	4.3	2.3	10	.21	5.2	0.033	0.8	6.25	SPR	CG	N
0.343	8.71	MM-76	.38	9.5	.233	5.9	192	34	.07	1.8	14	62	.30	7.7	0.055	1.4	4.50	SST	C	N
0.343	8.71	V-55	.38	9.5	.231	5.9	212	37	.08	2.0	17	74	.25	6.4	0.056	1.4	4.50	SST	CG	N
0.343	8.71	A-5	.41	10.3	.263	6.7	33	5.8	.19	4.7	6.1	27	.22	5.6	0.040	1.0	5.50	SST	CG	N
0.343	8.71	I-28	.41	10.3	.245	6.2	130	23	.10	2.5	13	57	.22	5.6	0.049	1.2	4.50	SPR	CG	N
0.343	8.71	1925	.44	11.1	.281	7.1	22	3.8	.22	5.7	4.9	22	.16	3.9	0.031	0.8	4.00	MW	C	Z
0.343	8.71	2950	.44	11.1	.275	7.0	33	5.7	.14	3.6	4.6	21	.17	4.3	0.034	0.9	4.00	SPR	C	Z
0.343	8.71	A12-3	.45	11.5	.263	6.7	48	8.4	.15	3.8	7.1	32	.23	5.8	0.040	1.0	4.75	SPR	C	N
0.343	8.71	W-97	.47	11.9	.275	7.0	19	3.4	.22	5.7	4.3	19	.20	5.2	0.034	0.9	5.00	SST	C	N
0.343	8.71	Q-98	.47	11.9	.265	6.7	16	2.8	.10	2.5	1.6	7.0	.37	9.4	0.039	1.0	8.50	SST	C	N
0.343	8.71	11451	.50	12.7	.305	7.7	2.4	.43	.40	10	.98	4.4	.10	2.5	0.019	0.5	4.25	MW	C	N
0.343	8.71	N-39	.50	12.7	.301	7.6	1.7	.29	.36	9.2	.60	2.7	.14	3.5	0.021	0.5	6.50	SST	CG	N
0.343	8.71	BB-56	.50	12.7	.295	7.5	4.3	.75	.36	9.0	1.5	6.7	.14	3.7	0.024	0.6	5.00	SST	C	N
0.343	8.71	2568	.50	12.7	.287	7.3	14	2.5	.26	6.5	3.6	16	.14	3.6	0.028	0.7	4.00	MW	C	Z
0.343	8.71	II-43	.50	12.7	.283	7.2	3.3	.58	.07	1.7	.21	.95	.44	11.0	0.030	0.8	13.5	MW	C	N
0.343	8.71	S-114	.50	12.7	.279	7.1	13	2.3	.27	6.8	3.6	16	.20	5.1	0.032	0.8	5.25	SST	C	N
0.343	8.71	I-86	.50	12.7	.275	7.0	19	3.3	.23	5.8	4.3	19	.20	5.2	0.034	0.9	5.00	SST	C	N
0.343	8.71	3453	.50	12.7	.273	6.9	25	4.3	.20	5.0	4.8	21	.21	5.3	0.035	0.9	5.00	SPR	C	GI
0.343	8.71	MM-64	.50	12.7	.263	6.7	23	4.0	.22	5.6	5.1	23	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.343	8.71	10882	.50	12.7	.251	6.4	89	16	.17	4.2	15	66	.22	5.6	0.046	1.2	4.75	MW	CG	N
0.343	8.71	MM-35	.50	12.7	.243	6.2	84	15	.15	3.8	13	57	.31	7.9	0.050	1.3	6.25	SPR	CG	Z
0.343	8.71	DD-30	.50	12.7	.243	6.2	79	14	.15	3.8	12	53	.30	7.6	0.050	1.3	6.00	SST	CG	N
0.343	8.71	G-93	.50	12.7	.235	6.0	110	19	.14	3.4	15	67	.32	8.2	0.054	1.4	6.00	SST	CG	N
0.343	8.71	BB-39	.50	12.7	.183	4.6	1177	206	.04	.99	46	204	.38	9.7	0.080	2.0	4.75	SPR	CG	N
0.343	8.71	B17-145	.53	13.5	.313	8.0	.25	.04	.36	9.2	.09	.40	.17	4.3	0.015	0.4	10.3	MW	C	N
0.343	8.71	L-89	.53	13.5	.299	7.6	2.9	.51	.39	9.9	1.1	5.0	.14	3.6	0.022	0.6	5.50	MW	C	Z
0.343	8.71	H-88	.53	13.5	.293	7.4	8.7	1.5	.30	7.5	2.6	11	.13	3.2	0.025	0.6	4.00	MW	C	N
0.343	8.71	A10-69	.53	13.5	.285	7.2	5.3	.93	.31	8.0	1.7	7.4	.22	5.5	0.029	0.7	7.50	SST	CG	N
0.343	8.71	3509	.53	13.5	.283	7.2	11	1.9	.37	9.3	4.0	18	.17	4.2	0.030	0.8	5.50	MW	CG	Z
0.343	8.71	Q-97	.53	13.5	.283	7.2	6.7	1.2	.29	7.4	2.0	8.7	.24	6.1	0.030	0.8	7.00	SST	C	N
0.343	8.71	II-32	.53	13.5	.279	7.1	9.4	1.6	.32	8.0	2.9	13	.22	5.5	0.032	0.8	6.75	SST	CG	N
0.343	8.71	B-67	.53	13.5	.279	7.1	10	1.8	.28	7.0	2.8	12	.26	6.5	0.032	0.8	7.00	HD	C	N
0.343	8.71	JJ-61	.53	13.5	.259	6.6	36	6.2	.22	5.5	7.7	34	.25	6.4	0.042	1.1	6.00	SST	CG	N
0.343	8.71	1655	.53	13.5	.189	4.8	716	125	.06	1.5	41	183	.44	11.3	0.077	2.0	5.75	SPR	CG	Z
0.343	8.71	10730	.56	14.3	.309	7.8	1.4	.24	.47	12	.65	2.9	.09	2.4	0.017	0.4	4.50	MW	C	N
0.343	8.71	S-1040	.56	14.3	.309	7.8	1.0	.18	.46	12	.46	2.1	.10	2.6	0.017	0.4	5.00	SST	C	N
0.343	8.71	S-3122	.56	14.3	.301	7.6	1.2	.21	.37	9.5	.45	2.0	.19	4.8	0.021	0.5	8.00	SST	C	N
0.343	8.71	11342	.56	14.3	.293	7.4	3.3	.57	.39	10	1.3	5.7	.17	4.3	0.025	0.6	6.75	SST	CG	N
0.343	8.71	K-71	.56	14.3	.291	7.4	4.3	.76	.39	9.8	1.7	7.5	.18	4.5	0.026	0.7	6.75	MW	CG	N
0.343	8.71	KK-76	.56	14.3	.279	7.1	14	2.5	.27	6.8	3.9	17	.21	5.3	0.032	0.8	5.50	SPR	C	N
0.343	8.71	G-87	.56	14.3	.261	6.6	37	6.5	.21	5.3	7.6	34	.25	6.2	0.041	1.0	6.00	SPR	CG	Z
0.343	8.71	Q-30	.63	15.9	.303	7.7	1.1	.20	.45	11	.51	2.3	.18	4.6	0.020	0.5	8.00	MW	C	N
0.343	8.71	A-60-A	.63	15.9	.293	7.4	1.9	.34	.35	8.9	.68	3.0	.28	7.0	0.025	0.6	10.0	SST	C	N
0.343	8.71	MM-68	.63	15.9	.279	7.1	8.7	1.5	.40	10	3.5	16	.22	5.7	0.032	0.8	7.00	SST	CG	N
0.343	8.71	N-46	.63	15.9	.273	6.9	18	3.2	.26	6.6	4.8	21	.21	5.3	0.035	0.9	6.00	SPR	C	GI
0.343	8.71	00-94	.63	15.9	.269	6.8	23	4.1	.23	5.8	5.3	24	.20	5.2	0.037	0.9	5.50	SST	CG	N
0.343	8.71	S-3119	.63	15.9	.261	6.6	37	6.4	.20	5.0	7.2	32	.27	6.8	0.041	1.0	5.50	SST	C	N
0.343	8.71	3814	.63	15.9	.253	6.4	45	7.8	.23	5.7	10	45	.36	9.1	0.045	1.1	7.00	SPR	C	Z
0.343	8.71	S-1043	.63	15.9	.247	6.3	57	10	.20	5.0	11	50	.31	7.9	0.048	1.2	6.50	SST	CG	N
0.343	8.71	B2-11	.63	16.0	.253	6.4	24	4.2	.14	3.5	3.3	15	.50	12.6	0.045	1.1	10.0	SST	CL	N
0.343	8.71	L-78	.66	16.7	.267	6.8	18	3.1	.3											




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.343	8.71	YY-59	.69	17.4	.241	6.1	130	23	.10	2.6	13	60	.26	6.5	0.051	1.3	5.00	SPR	CG	Z
0.343	8.71	B-86	.72	18.2	.299	7.6	2.2	.39	.56	14	1.2	5.5	.15	3.9	0.022	0.6	6.00	SST	C	N
0.343	8.71	10106	.72	18.3	.263	6.7	33	5.8	.21	5.5	7.1	32	.28	7.1	0.040	1.0	6.00	SPR	C	N
0.343	8.71	S-1094	.75	19.1	.317	8.1	.14	.02	.62	16	.09	.39	.13	3.3	0.013	0.3	9.00	SST	C	N
0.343	8.71	S-1002	.75	19.1	.303	7.7	1.5	.26	.61	15	.91	4.0	.14	3.6	0.020	0.5	6.00	SST	C	N
0.343	8.71	1527	.75	19.1	.297	7.5	2.7	.48	.58	15	1.6	7.0	.17	4.4	0.023	0.6	6.50	MW	C	Z
0.343	8.71	S-309	.75	19.1	.293	7.4	3.6	.63	.48	12	1.7	7.7	.18	4.6	0.025	0.6	6.25	SST	C	N
0.343	8.71	PP-58	.75	19.1	.287	7.3	6.1	1.1	.39	10	2.4	11	.17	4.3	0.028	0.7	6.00	SST	CG	N
0.343	8.71	H-79	.75	19.1	.283	7.2	8.3	1.4	.36	9.1	3.0	13	.18	4.6	0.030	0.8	6.00	SST	C	N
0.343	8.71	GG-98	.75	19.1	.275	7.0	9.4	1.7	.44	11	4.2	19	.31	7.8	0.034	0.9	8.00	SST	C	N
0.343	8.71	A10-47	.75	19.1	.269	6.8	17	2.9	.34	8.7	5.7	25	.28	7.2	0.037	0.9	7.75	SPR	CG	N
0.343	8.71	10804	.75	19.1	.267	6.8	18	3.1	.35	8.8	6.1	27	.30	7.7	0.038	1.0	8.00	SPR	CG	BO
0.343	8.71	S-1180	.75	19.1	.267	6.8	15	2.7	.37	9.5	5.7	25	.34	8.7	0.038	1.0	8.00	SST	C	N
0.343	8.71	I-20	.75	19.1	.257	6.5	29	5.0	.29	7.3	8.2	37	.32	8.2	0.043	1.1	7.50	SST	CG	N
0.343	8.71	GG-70	.75	19.1	.243	6.2	79	14	.15	3.8	12	53	.30	7.6	0.050	1.3	6.00	SST	CG	N
0.343	8.71	CC-100	.75	19.1	.239	6.1	62	11	.22	5.5	13	60	.42	10.6	0.052	1.3	8.00	SST	CG	N
0.343	8.71	Z-57	.75	19.1	.229	5.8	100	17	.19	4.7	19	83	.48	12.3	0.057	1.4	8.50	SPR	CG	Z
0.343	8.71	B-100	.75	19.1	.227	5.8	108	19	.18	4.6	20	87	.49	12.5	0.058	1.5	8.50	SPR	CG	N
0.343	8.71	B14-35	.75	19.1	.223	5.7	117	21	.18	4.7	22	96	.54	13.7	0.060	1.5	9.00	SPR	CG	N
0.343	8.71	FF-69	.75	19.1	.223	5.7	113	20	.19	4.8	22	96	.56	14.1	0.060	1.5	9.25	SPR	CG	Z
0.343	8.71	S-3127	.75	19.1	.219	5.6	145	25	.15	3.9	22	99	.48	12.2	0.062	1.6	7.75	SST	CG	N
0.343	8.71	00-36	.78	19.8	.303	7.7	1.5	.27	.63	16	.96	4.3	.15	3.8	0.020	0.5	6.50	MW	C	N
0.343	8.71	10817	.78	19.8	.275	7.0	14	2.5	.44	11	6.4	29	.22	5.6	0.034	0.9	6.50	MW	CG	Z
0.343	8.71	I-90	.78	19.8	.255	6.5	33	5.7	.27	6.9	8.8	39	.33	8.4	0.044	1.1	7.50	SST	CG	N
0.343	8.71	12641	.78	19.8	.241	6.1	49	8.5	.26	6.6	13	56	.46	11.7	0.051	1.3	9.00	SST	CG	N
0.343	8.71	A-92	.81	20.6	.311	7.9	.60	.10	.69	18	.41	1.8	.12	3.0	0.016	0.4	6.50	MW	C	N
0.343	8.71	KK-84	.81	20.6	.287	7.3	2.9	.51	.49	12	1.4	6.3	.32	8.2	0.028	0.7	10.5	SST	C	N
0.343	8.71	M-120	.81	20.6	.277	7.0	17	2.9	.24	6.0	3.9	17	.20	5.0	0.033	0.8	5.00	SST	C	N
0.343	8.71	VW-49	.81	20.6	.277	7.0	17	2.9	.24	6.0	3.9	17	.20	5.0	0.033	0.8	5.00	SST	C	N
0.343	8.71	XX-22	.81	20.6	.277	7.0	7.6	1.3	.47	12	3.6	16	.35	8.8	0.033	0.8	9.50	SPR	C	GI
0.343	8.71	S-1232	.81	20.6	.273	6.9	12	2.0	.39	9.8	4.5	20	.26	6.7	0.035	0.9	7.50	SST	CG	N
0.343	8.71	3020	.81	20.6	.235	6.0	84	15	.19	4.8	16	71	.49	12.3	0.054	1.4	8.00	HD	C	Z
0.343	8.71	A-6	.81	20.6	.223	5.7	137	24	.16	4.0	22	96	.48	12.2	0.060	1.5	8.00	HD	CG	Z
0.343	8.71	B5-17	.84	21.4	.279	7.1	13	2.2	.31	7.8	3.9	17	.22	5.7	0.032	0.8	6.00	SPR	C	N
0.343	8.71	A10-66	.84	21.4	.219	5.6	160	28	.15	3.8	24	105	.50	12.6	0.062	1.6	8.00	SPR	CG	Z
0.343	8.71	00-59	.88	22.2	.311	7.9	.29	.05	.70	18	.20	.91	.18	4.5	0.016	0.4	10.0	SST	C	N
0.343	8.71	S-3105	.88	22.2	.303	7.7	.79	.14	.67	17	.53	2.3	.21	5.3	0.020	0.5	9.50	SST	C	N
0.343	8.71	II-76	.88	22.2	.303	7.7	.34	.06	.42	11	.14	.63	.46	11.7	0.020	0.5	22.0	MW	C	N
0.343	8.71	HH-25	.88	22.2	.293	7.4	3.9	.68	.67	17	2.6	11	.19	4.8	0.025	0.6	6.50	MW	C	N
0.343	8.71	S-3081	.88	22.2	.293	7.4	3.8	.66	.46	12	1.7	7.7	.18	4.4	0.025	0.6	6.00	SST	C	N
0.343	8.71	BB-72	.88	22.2	.293	7.4	2.4	.43	.67	17	1.6	7.2	.21	5.2	0.025	0.6	8.25	SST	CG	N
0.343	8.71	L-77	.88	22.2	.285	7.2	4.4	.77	.60	15	2.6	12	.28	7.0	0.029	0.7	9.50	MW	CG	GI
0.343	8.71	Z-1	.88	22.2	.283	7.2	6.0	1.1	.49	13	3.0	13	.26	6.5	0.030	0.8	7.50	SST	C	N
0.343	8.71	A15-39	.88	22.2	.281	7.1	7.8	1.4	.42	11	3.3	15	.22	5.5	0.031	0.8	7.00	SST	CG	N
0.343	8.71	Q-62	.88	22.2	.273	6.9	7.6	1.3	.51	13	3.8	17	.37	9.3	0.035	0.9	10.5	SST	CG	N
0.343	8.71	11398	.88	22.2	.269	6.8	12	2.1	.44	11	5.3	24	.37	9.4	0.037	0.9	9.00	SST	C	N
0.343	8.71	B6-23	.88	22.2	.269	6.8	16	2.9	.34	8.7	5.7	25	.28	7.2	0.037	0.9	7.70	SPR	CG	N
0.343	8.71	0-78	.88	22.2	.269	6.8	16	2.7	.36	9.2	5.7	25	.33	8.5	0.037	0.9	8.00	SPR	C	GI
0.343	8.71	10064	.88	22.2	.261	6.6	20	3.4	.39	9.9	7.6	34	.39	9.9	0.041	1.0	9.50	SPR	CG	Z
0.343	8.71	3520	.88	22.2	.243	6.2	65	11	.27	6.9	18	79	.38	9.5	0.050	1.3	7.50	MW	CG	Z
0.343	8.71	MM-95	.88	22.2	.203	5.2	242	42	.13	3.3	32	141	.63	16.0	0.070	1.8	9.00	SPR	CG	N
0.343	8.71	MM-86	.88	22.2	.199	5.1	307	54	.10	2.7	32	143	.54	13.7	0.072	1.8	7.50	SST	CG	N
0.343	8.71	B12-25	.88	22.2	.191	4.9	315	55	.12	2.9	36	161	.76	19.3	0.076	1.9	10.0	SPR	CG	N
0.343	8.71	H-82	.91	23.0	.261	6.6	11	1.8	.21	5.3	2.2	9.8	.70	17.7	0.041	1.0	16.0	SPR	C	Z
0.343	8.71	2604	.91	23.0	.249	6.3	39	6.8	.41	10	16	70	.42	10.7	0.047	1.2	9.00	MW	CG	Z
0.343	8.71	0-145	.91	23.0	.245	6.2	59	10	.22	5.5	13	57	.37	9.3	0.049	1.2	7.50	SPR	CG	N
0.343	8.71	Z-4	.94	23.8	.293	7.4	2.5	.44	.69	17	1.7	7.6	.25	6.4	0.025	0.6	9.00	MW	C	N
0.343	8.71	U-37	.94	23.8	.273	6.9	11	1.9	.42	11	4.5	20	.28	7.1	0.035	0.9	8.00	SST	CG	N
0.343	8.71	JJ-86	.94	23.8	.259	6.6	21	3.6	.40	10	8.2	36	.46	11.7	0.042	1.1	10.0	SPR	C	Z
0.343	8.71	L-69	.94	23.8	.247	6.3	42	7.4	.28	7.2	12	54	.48	12.2	0.048	1.2	9.00	SPR	C	Z
0.343	8.71	PP-29	.94	23.8	.203	5.2	201	35	.15	3.8	30	132	.67	16.9	0.070	1.8	9.50	SST	CG	N
0.343	8.71	PP-28	.97	24.6	.263	6.7	20	3.6	.35	8.9	7.1	32	.34	8.6	0.040	1.0	8.50	SPR	CG	Z
0.343	8.71	L-13	.97	24.6	.249	6.3	34	5.9	.34	8.6	11	51	.52	13.1	0.047	1.2	10.0	SPR	C	Z
0.343	8.71	3658	1.00	25.4	.305	7.7	.79	.14	.81	21	.64	2.8	.19	4.8	0.019	0.5	9.00	MW	C	GI
0.343	8.71	11469	1.00	25.4	.303	7.7	1.4	.24	.84	21	1.1	5.1	.16	4.1	0.020	0.5	7.00	MW	C	N
0.343	8.71	11277	1.00	25.4	.285	7.2	3.8	.66	.66	17	2.5	11	.34	8.7	0.029	0.7	10.8	MW	C	N
0.343	8.71	B4-13	1.00	25.4	.283	7.2	5.4	.95	.73	19	4.0	18	.27	6.9	0.030	0.8	9.00	MW	CG	N
0.343	8.71	B-94	1.00	25.4	.279	7.1	7.7	1.4	.50	13	3.9	17	.27	6.9	0.032	0.8	8.50	HD	CG	Z
0.343	8.71	3639	1.00	25.4	.267	6.8	15	2.6	.56	14	8.5	38	.38	9.7	0.038	1.0</				





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.343	8.71	PP-25	1.03	26.2	.283	7.2	4.2	.74	.67	17	2.8	13	.36	9.1	0.030	0.8	11.0	MW	C	Z
0.343	8.71	S-1056	1.06	27.0	.291	7.4	2.2	.39	.78	20	1.7	7.7	.29	7.3	0.026	0.7	10.0	SST	C	N
0.343	8.71	S-1456	1.06	27.0	.281	7.1	4.2	.74	.72	18	3.0	14	.34	8.7	0.031	0.8	11.0	SST	CG	N
0.343	8.71	A14-6	1.06	27.0	.277	7.0	6.8	1.2	.58	15	3.9	17	.31	8.0	0.033	0.8	9.50	SST	CG	N
0.343	8.71	S-1695	1.06	27.0	.273	6.9	11	1.9	.42	11	4.5	20	.32	8.0	0.035	0.9	8.00	SST	C	N
0.343	8.71	S-1347	1.06	27.0	.269	6.8	8.6	1.5	.62	16	5.3	24	.43	10.8	0.037	0.9	11.5	SST	CG	N
0.343	8.71	L-53	1.06	27.0	.263	6.7	19	3.3	.38	9.6	7.1	32	.36	9.1	0.040	1.0	9.00	SPR	CG	Z
0.343	8.71	4202	1.06	27.0	.253	6.4	25	4.3	.41	10	10	45	.54	13.7	0.045	1.1	11.0	SPR	C	Z
0.343	8.71	I-21	1.06	27.0	.253	6.4	17	2.9	.40	10	6.7	30	.66	16.9	0.045	1.1	13.8	SST	C	N
0.343	8.71	CC-85	1.06	27.0	.235	6.0	72	13	.22	5.6	16	71	.49	12.3	0.054	1.4	9.00	SPR	CG	Z
0.343	8.71	00-70	1.13	28.6	.283	7.2	4.2	.74	.71	18	3.0	13	.30	7.6	0.030	0.8	10.0	SST	CG	N
0.343	8.71	M-76	1.13	28.6	.273	6.9	9.2	1.6	.52	13	4.8	21	.35	8.9	0.035	0.9	10.0	SPR	CG	N
0.343	8.71	S-1057	1.13	28.6	.267	6.8	10	1.8	.56	14	5.7	25	.42	10.6	0.038	1.0	11.0	SST	CG	N
0.343	8.71	10387	1.19	30.2	.299	7.6	1.3	.22	.97	25	1.2	5.5	.22	5.6	0.022	0.6	10.0	MW	CG	Z
0.343	8.71	10273	1.19	30.2	.219	5.6	128	22	.19	4.7	24	105	.59	15.0	0.062	1.6	9.50	SPR	CG	Z
0.343	8.71	W-11	1.22	31.0	.273	6.9	7.1	1.2	.63	16	4.5	20	.39	9.8	0.035	0.9	11.0	SST	CG	N
0.343	8.71	S-1223	1.25	31.8	.279	7.1	4.4	.76	.82	21	3.6	16	.42	10.6	0.032	0.8	12.0	SST	C	N
0.343	8.71	12499	1.25	31.8	.275	7.0	8.7	1.5	.49	13	4.3	19	.32	8.2	0.034	0.9	8.50	SST	C	N
0.343	8.71	11256	1.25	31.8	.273	6.9	11	2.0	.59	15	6.6	30	.33	8.4	0.035	0.9	8.50	MW	C	Z
0.343	8.71	CC-7	1.25	31.8	.259	6.6	15	2.6	.55	14	8.2	36	.55	13.9	0.042	1.1	13.0	SPR	CG	GI
0.343	8.71	11257	1.25	31.8	.259	6.6	18	3.2	.42	11	7.7	34	.46	11.7	0.042	1.1	10.0	SST	C	N
0.343	8.71	B2-40	1.25	31.8	.255	6.5	23	4.0	.39	9.9	8.8	39	.47	12.0	0.044	1.1	9.75	SST	C	N
0.343	8.71	3842	1.25	31.8	.159	4.0	724	127	.09	2.2	64	285	1.01	25.7	0.092	2.3	11.0	SPR	CG	GI
0.343	8.71	3505	1.28	32.5	.273	6.9	7.4	1.3	.83	21	6.1	27	.46	11.6	0.035	0.9	12.0	MW	C	Z
0.343	8.71	B9-23	1.31	33.3	.257	6.5	16	2.8	.55	14	8.8	39	.62	15.8	0.043	1.1	13.5	SPR	C	N
0.343	8.71	L-44	1.38	34.9	.295	7.5	1.6	.28	1.0	26	1.6	7.2	.26	6.7	0.024	0.6	10.0	SST	C	N
0.343	8.71	3884	1.38	34.9	.289	7.3	2.2	.39	1.0	25	2.2	9.8	.38	9.6	0.027	0.7	13.0	MW	C	Z
0.343	8.71	3457	1.38	34.9	.279	7.1	7.7	1.4	.70	18	5.4	24	.30	7.7	0.032	0.8	8.50	MW	C	Z
0.343	8.71	L-32	1.44	36.5	.293	7.4	1.4	.24	1.0	27	1.4	6.4	.39	9.9	0.025	0.6	14.6	MW	C	Z
0.343	8.71	2594	1.44	36.5	.249	6.3	27	4.7	.42	11	11	51	.56	14.3	0.047	1.2	12.0	HD	CG	Z
0.343	8.71	10519	1.47	37.3	.259	6.6	14	2.4	.59	15	8.2	36	.62	15.7	0.042	1.1	13.8	SPR	C	Z
0.343	8.71	S-3101	1.50	38.1	.293	7.4	1.4	.25	1.2	29	1.6	7.3	.34	8.7	0.025	0.6	12.8	SST	C	N
0.343	8.71	1951	1.50	38.1	.283	7.2	3.5	.60	1.1	27	3.7	17	.42	10.7	0.030	0.8	13.0	MW	C	Z
0.343	8.71	12630	1.50	38.1	.283	7.2	3.8	.66	1.1	28	4.2	19	.39	9.9	0.030	0.8	12.0	MW	C	Z
0.343	8.71	3890	1.50	38.1	.273	6.9	7.0	1.2	.68	17	4.8	21	.47	12.0	0.035	0.9	12.5	SPR	C	Z
0.343	8.71	UU-47	1.50	38.1	.269	6.8	6.3	1.1	.83	21	5.2	23	.67	16.9	0.037	0.9	17.0	SPR	C	Z
0.343	8.71	5	1.50	38.1	.249	6.3	23	3.9	.50	13	11	51	.71	17.9	0.047	1.2	14.0	HD	C	Z
0.343	8.71	S-879	1.50	38.1	.249	6.3	19	3.3	.57	15	11	47	.69	17.5	0.047	1.2	14.8	SST	CG	N
0.343	8.71	11453	1.50	38.1	.219	5.6	113	20	.21	5.3	24	105	.65	16.5	0.062	1.6	10.5	HD	CG	Z
0.343	8.71	B2-53	1.50	38.1	.213	5.4	96	17	.28	7.2	27	120	.94	24.0	0.065	1.7	14.5	SPR	CG	N
0.343	8.71	12405	1.53	38.9	.311	7.9	.35	.06	1.4	35	.47	2.1	.17	4.4	0.016	0.4	9.75	MW	C	Z
0.343	8.71	11546	1.53	38.9	.257	6.5	17	3.0	.51	13	8.8	39	.58	14.7	0.043	1.1	12.5	SPR	CG	Z
0.343	8.71	10188	1.56	39.7	.303	7.7	.49	.09	1.2	31	.60	2.7	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.343	8.71	QQ-36	1.56	39.7	.271	6.9	5.6	.97	.91	23	5.1	23	.65	16.5	0.036	0.9	17.0	SPR	C	Z
0.343	8.71	S-1099	1.56	39.7	.247	6.3	18	3.1	.64	16	11	50	.79	20.1	0.048	1.2	16.5	SST	CG	N
0.343	8.71	A15-36	1.56	39.7	.241	6.1	23	4.0	.55	14	13	56	.87	22.0	0.051	1.3	17.0	SST	CG	N
0.343	8.71	S-210	1.59	40.5	.287	7.3	1.6	.27	1.1	27	1.7	7.4	.53	13.5	0.028	0.7	18.0	SST	C	N
0.343	8.71	S-452	1.63	41.3	.303	7.7	.20	.04	.98	25	.20	.87	.65	16.5	0.020	0.5	31.5	SST	C	N
0.343	8.71	S-15	1.63	41.3	.273	6.9	6.4	1.1	.70	18	4.5	20	.46	11.6	0.035	0.9	12.0	SST	C	N
0.343	8.71	HH-58	1.63	41.3	.263	6.7	9.4	1.7	.75	19	7.1	32	.64	16.3	0.040	1.0	16.0	SPR	CG	N
0.343	8.71	KK-73	1.63	41.3	.243	6.2	27	4.7	.47	12	13	57	.76	19.4	0.050	1.3	15.3	SPR	CG	Z
0.343	8.71	S-1384	1.75	44.5	.303	7.7	.46	.08	1.4	36	.65	2.9	.32	8.1	0.020	0.5	15.0	SST	C	N
0.343	8.71	S-1492	1.81	46.0	.247	6.3	14	2.5	.79	20	11	50	.96	24.4	0.048	1.2	20.0	SST	CG	N
0.343	8.71	2933	1.81	46.0	.227	5.8	40	7.0	.49	12	20	87	1.13	28.7	0.058	1.5	19.5	SPR	CG	Z
0.343	8.71	2683	1.91	48.4	.227	5.8	50	8.8	.39	9.9	20	87	.93	23.6	0.058	1.5	16.0	SPR	CG	Z
0.343	8.71	11199	2.00	50.8	.293	7.4	.70	.12	1.3	33	.91	4.0	.70	17.8	0.025	0.6	27.0	MW	C	Z
0.343	8.71	1819	2.00	50.8	.279	7.1	3.1	.55	1.4	35	4.4	19	.61	15.4	0.032	0.8	18.0	MW	C	Z
0.343	8.71	B14-27	2.00	50.8	.275	7.0	4.3	.76	1.1	27	4.6	21	.61	15.5	0.034	0.9	17.0	SPR	C	Z
0.343	8.71	M-10	2.00	50.8	.271	6.9	4.4	.77	1.2	30	5.2	23	.79	20.1	0.036	0.9	21.0	SPR	C	N
0.343	8.71	A-76	2.00	50.8	.263	6.7	7.8	1.4	.91	23	7.1	32	.76	19.3	0.040	1.0	19.0	SPR	CG	Z
0.343	8.71	CC-71	2.00	50.8	.263	6.7	9.4	1.7	.75	19	7.1	32	.68	17.3	0.040	1.0	16.0	SPR	C	N
0.343	8.71	3442	2.00	50.8	.209	5.3	73	13	.41	10	29	131	1.41	35.7	0.067	1.7	21.0	SPR	CG	Z
0.343	8.71	11466	2.13	54.0	.293	7.4	.69	.12	1.5	38	1.0	4.6	.64	16.2	0.025	0.6	24.5	SST	C	N
0.343	8.71	VV-30	2.13	54.0	.249	6.3	15	2.6	.76	19	11	51	.94	23.9	0.047	1.2	20.0	HD	CG	N
0.343	8.71	10437	2.16	54.8	.293	7.4	.78	.14	1.5	39	1.2	5.2	.64	16.2	0.025	0.6	24.5	MW	C	Z
0.343	8.71	11722	2.16	54.8	.289	7.3	2.2	.39	1.5	37	3.2	14	.38	9.6	0.027	0.7	13.0	MW	C	Z
0.343	8.71	Q-38	2.25	57.2	.291	7.4	.87	.15	1.6	39	1.3	6.0	.70	17.7	0.026	0.7	25.8	MW	C	N
0.343	8.71	S-225	2.28	57.9	.191	4.9	128	22	.29	7.4	37	166	1.48	37.6	0.076	1.9	19.5	SST	CG	N
0.343	8.71	3691	2.34	59.5	.289	7.3	1.6	.28</												




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.343	8.71	B8-55	4.88	123.8	.247	6.3	8.4	1.5	1.4	37	12	54	1.85	46.9	0.048	1.2	37.5	SPR	C	Z
0.343	8.71	10546	5.25	133.4	.243	6.2	8.5	1.5	1.5	38	13	57	2.25	57.2	0.050	1.3	44.0	SPR	C	Z
0.343	8.71	1912	5.75	146.1	.263	6.7	2.5	.44	2.8	72	7.1	32	2.23	56.6	0.040	1.0	54.8	SPR	C	GI
0.350	8.89	B4-63	.62	15.8	.286	7.3	4.3	.75	.21	5.2	.88	3.9	.42	10.6	0.032	0.8	13.0	MW	CG	BO
0.350	8.89	12705	1.30	32.9	.260	6.6	24	4.2	.38	9.7	9.2	41	.47	12.0	0.045	1.1	9.50	SST	C	N
0.350	8.89	12752	1.87	47.5	.308	7.8	.49	.09	1.5	37	.72	3.2	.40	10.1	0.021	0.5	18.0	MW	C	N
0.360	9.14	MM-63	.25	6.4	.340	8.6	.07	.01	.18	4.6	.01	.06	.07	1.8	0.010	0.3	6.00	SST	C	N
0.360	9.14	2899	.25	6.4	.330	8.4	.60	.10	.16	4.1	.10	.42	.09	2.3	0.015	0.4	5.00	MW	C	Z
0.360	9.14	I-27	.25	6.4	.296	7.5	43	7.5	.09	2.2	3.7	16	.13	3.3	0.032	0.8	3.00	HD	C	N
0.360	9.14	L-66	.25	6.4	.284	7.2	91	16	.06	1.6	5.8	26	.11	2.9	0.038	1.0	3.00	SPR	CG	Z
0.360	9.14	I-53	.25	6.4	.280	7.1	99	17	.06	1.6	6.4	28	.16	4.1	0.040	1.0	3.00	SST	C	N
0.360	9.14	AA-93	.25	6.4	.266	6.8	201	35	.05	1.3	10	45	.14	3.6	0.047	1.2	3.00	SST	CG	N
0.360	9.14	PP-39	.34	8.7	.320	8.1	1.3	.23	.22	5.7	.29	1.3	.12	3.0	0.020	0.5	6.00	SST	CG	N
0.360	9.14	HH-45	.34	8.7	.300	7.6	13	2.3	.21	5.3	2.7	12	.14	3.4	0.030	0.8	4.50	MW	CG	Z
0.360	9.14	B1-1	.38	9.5	.314	8.0	3.5	.62	.24	6.0	.84	3.7	.14	3.5	0.023	0.6	5.00	MW	CG	Z
0.360	9.14	10849	.38	9.5	.296	7.5	25	4.3	.21	5.3	5.1	23	.12	3.0	0.032	0.8	3.75	MW	CG	Z
0.360	9.14	G-54	.38	9.5	.292	7.4	28	4.9	.16	4.0	4.4	20	.17	4.3	0.034	0.9	4.00	SPR	C	N
0.360	9.14	M-142	.38	9.5	.286	7.3	40	7.1	.13	3.4	5.4	24	.19	4.7	0.037	0.9	4.00	SPR	C	N
0.360	9.14	2502	.38	9.5	.256	6.5	182	32	.10	2.6	19	84	.21	5.3	0.052	1.3	4.00	MW	CG	Z
0.360	9.14	71064	.38	9.7	.296	7.5	25	4.4	.20	5.2	5.1	23	.12	3.0	0.032	0.8	3.75	MW	CG	N
0.360	9.14	71064S	.38	9.7	.296	7.5	21	3.7	.16	4.1	3.4	15	.12	3.0	0.032	0.8	3.75	SST	CG	N
0.360	9.14	NN-35	.41	10.3	.300	7.6	7.1	1.2	.23	5.7	1.6	7.1	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.360	9.14	TT-33	.41	10.3	.288	7.3	19	3.3	.16	4.1	3.1	14	.24	6.2	0.036	0.9	5.75	SPR	C	Z
0.360	9.14	J-14	.41	10.3	.278	7.1	32	5.5	.12	3.0	3.8	17	.29	7.3	0.041	1.0	6.00	SPR	C	Z
0.360	9.14	LL-67	.41	10.3	.270	6.9	84	15	.11	2.7	9.0	40	.18	4.6	0.045	1.1	4.00	SST	CG	N
0.360	9.14	G-51	.41	10.3	.250	6.4	187	33	.09	2.2	16	71	.25	6.3	0.055	1.4	4.50	SPR	CG	Z
0.360	9.14	K-87	.41	10.3	.222	5.6	594	104	.05	1.3	31	137	.29	7.4	0.069	1.8	4.25	SPR	CG	Z
0.360	9.14	10956	.44	11.1	.314	8.0	4.7	.83	.32	8.1	1.5	6.6	.12	3.1	0.023	0.6	4.25	MW	C	N
0.360	9.14	II-83	.44	11.1	.298	7.6	5.5	.95	.16	4.0	.87	3.9	.28	7.1	0.031	0.8	8.00	SST	C	N
0.360	9.14	G-45	.44	11.1	.282	7.2	41	7.1	.16	3.9	6.3	28	.21	5.4	0.039	1.0	4.50	SPR	C	Z
0.360	9.14	I-15	.44	11.1	.280	7.1	45	7.9	.15	3.8	6.8	30	.18	4.6	0.040	1.0	4.50	SPR	CG	Z
0.360	9.14	FF-41	.44	11.1	.276	7.0	47	8.2	.17	4.3	7.8	35	.21	5.3	0.042	1.1	5.00	SPR	CG	Z
0.360	9.14	S-1505	.44	11.1	.266	6.8	67	12	.15	3.9	10	45	.24	6.0	0.047	1.2	5.00	SST	CG	N
0.360	9.14	S-1100	.44	11.1	.262	6.7	60	11	.14	3.7	8.7	39	.29	7.5	0.049	1.2	6.00	SST	CG	N
0.360	9.14	AA-95	.44	11.1	.262	6.7	93	16	.13	3.4	12	55	.25	6.2	0.049	1.2	5.00	SPR	CG	N
0.360	9.14	JJ-56	.44	11.1	.250	6.4	187	33	.09	2.2	16	71	.30	7.7	0.055	1.4	4.50	SPR	C	N
0.360	9.14	71027	.44	11.2	.308	7.8	10	1.8	.27	6.9	2.8	12	.10	2.5	0.026	0.7	3.75	MW	CG	N
0.360	9.14	71027S	.44	11.2	.308	7.8	8.7	1.5	.21	5.4	1.9	8.3	.10	2.5	0.026	0.7	3.75	SST	CG	N
0.360	9.14	71046	.44	11.2	.302	7.7	15	2.6	.26	6.7	3.8	17	.11	2.9	0.029	0.7	3.88	MW	CG	N
0.360	9.14	71046S	.44	11.2	.302	7.7	12	2.2	.21	5.2	2.6	11	.11	2.9	0.029	0.7	3.88	SST	CG	N
0.360	9.14	71065	.44	11.2	.296	7.5	21	3.6	.25	6.3	5.1	23	.13	3.3	0.032	0.8	4.00	MW	CG	N
0.360	9.14	71065S	.44	11.2	.296	7.5	18	3.1	.19	4.9	3.4	15	.13	3.3	0.032	0.8	4.00	SST	CG	N
0.360	9.14	71083	.44	11.2	.290	7.4	28	4.9	.23	5.7	6.3	28	.15	3.8	0.035	0.9	4.25	MW	CG	N
0.360	9.14	71083S	.44	11.2	.290	7.4	24	4.2	.18	4.6	4.3	19	.15	3.8	0.035	0.9	4.25	SST	CG	N
0.360	9.14	71101	.44	11.2	.284	7.2	38	6.6	.21	5.4	8.1	36	.17	4.2	0.038	1.0	4.38	MW	CG	N
0.360	9.14	71101S	.44	11.2	.284	7.2	32	5.6	.17	4.3	5.5	24	.17	4.2	0.038	1.0	4.38	SST	CG	N
0.360	9.14	71119	.44	11.2	.280	7.1	45	7.9	.21	5.3	9.4	42	.18	4.6	0.040	1.0	4.50	MW	CG	N
0.360	9.14	71119S	.44	11.2	.280	7.1	38	6.7	.17	4.2	6.4	28	.18	4.6	0.040	1.0	4.50	SST	CG	N
0.360	9.14	71137	.44	11.2	.276	7.0	57	10	.19	4.8	11	48	.19	4.8	0.042	1.1	4.50	MW	CG	N
0.360	9.14	71137S	.44	11.2	.276	7.0	48	8.5	.15	3.8	7.3	33	.19	4.8	0.042	1.1	4.50	SST	CG	N
0.360	9.14	71155	.44	11.2	.270	6.9	77	13	.17	4.4	13	59	.20	5.1	0.045	1.1	4.50	MW	CG	N
0.360	9.14	71155S	.44	11.2	.270	6.9	65	11	.14	3.5	9.0	40	.20	5.1	0.045	1.1	4.50	SST	CG	N
0.360	9.14	71174	.44	11.2	.266	6.8	93	16	.16	4.1	15	67	.21	5.4	0.047	1.2	4.50	MW	CG	N
0.360	9.14	71174S	.44	11.2	.266	6.8	79	14	.13	3.3	10	45	.21	5.4	0.047	1.2	4.50	SST	CG	N
0.360	9.14	71196	.44	11.2	.262	6.7	109	19	.16	4.0	17	76	.22	5.6	0.049	1.2	4.50	MW	CG	N
0.360	9.14	71196S	.44	11.2	.262	6.7	93	16	.12	3.2	12	51	.22	5.6	0.049	1.2	4.50	SST	CG	N
0.360	9.14	71218	.44	11.2	.258	6.6	127	22	.14	3.6	18	80	.24	6.0	0.051	1.3	4.63	MW	CG	N
0.360	9.14	71218S	.44	11.2	.258	6.6	108	19	.11	2.9	12	54	.24	6.0	0.051	1.3	4.63	SST	CG	N
0.360	9.14	71240	.44	11.2	.250	6.4	175	31	.13	3.2	22	99	.25	6.5	0.055	1.4	4.63	MW	CG	N
0.360	9.14	71240S	.44	11.2	.250	6.4	149	26	.10	2.6	15	67	.25	6.5	0.055	1.4	4.63	SST	CG	N
0.360	9.14	71262	.44	11.2	.242	6.1	238	42	.11	2.9	27	121	.27	6.9	0.059	1.5	4.63	MW	CG	N
0.360	9.14	71262S	.44	11.2	.242	6.1	202	35	.09	2.3	18	82	.27	6.9	0.059	1.5	4.63	SST	CG	N
0.360	9.14	M-71	.47	11.9	.286	7.3	27	4.7	.20	5.1	5.4	24	.19	4.7	0.037	0.9	5.00	SPR	CG	Z
0.360	9.14	EE-72	.47	11.9	.276	7.0	56	9.8	.14	3.5	7.8	35	.19	4.8	0.042	1.1	4.50	SPR	CG	Z
0.360	9.14	A10-31	.47	11.9	.244	6.2	93	16	.15	3.8	14	61	.32	8.1	0.058	1.5	5.50	PB	CG	N
0.360	9.14	S-133	.47	11.9	.234	5.9	258	45	.09	2.2	22	99	.32	8.0	0.063	1.6	5.00	SST	CG	N
0.360	9.14	LL-6	.50	12.7	.320	8.1	1.0	.17	.34	8.5	.33	1.5	.17	4.2	0.020	0.5	7.25	SST	C	N
0.360	9.14	A-52	.50	12.7	.310	7.9	7.5	1.3	.33	8.3	2.5	11	.13	3.2	0.025	0.6	4.00	MW	C	Z
0.360	9.14	10076	.50	12.7	.308	7.8	8.9	1.6	.31	7.9	2.8	12	.10	2.6	0.					



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.360	9.14	71084S	.50	12.7	.290	7.4	20	3.6	.21	5.3	4.3	19	.16	4.1	0.035	0.9	4.63	SST	CG	N
0.360	9.14	10122	.50	12.7	.285	7.2	27	4.7	.21	5.3	5.6	25	.19	4.7	0.037	0.9	5.00	SPR	CG	Z
0.360	9.14	K-79	.50	12.7	.284	7.2	32	5.5	.17	4.4	5.5	24	.21	5.3	0.038	1.0	4.50	SST	C	N
0.360	9.14	71102	.50	12.7	.284	7.2	33	5.8	.24	6.2	8.1	36	.18	4.6	0.038	1.0	4.75	MW	CG	N
0.360	9.14	71102S	.50	12.7	.284	7.2	28	4.9	.19	4.9	5.5	24	.18	4.6	0.038	1.0	4.75	SST	CG	N
0.360	9.14	71120	.50	12.7	.280	7.1	39	6.8	.24	6.2	9.4	42	.20	5.0	0.040	1.0	4.88	MW	CG	N
0.360	9.14	71120S	.50	12.7	.280	7.1	33	5.8	.19	4.9	6.4	28	.20	5.0	0.040	1.0	4.88	SST	CG	N
0.360	9.14	A10-7	.50	12.7	.278	7.1	37	6.5	.18	4.7	6.8	30	.21	5.2	0.041	1.0	5.00	SST	CG	N
0.360	9.14	WW-67	.50	12.7	.278	7.1	28	4.9	.23	5.9	6.6	29	.27	6.8	0.041	1.0	6.50	SPR	CG	Z
0.360	9.14	B12-23	.50	12.7	.278	7.1	42	7.4	.17	4.4	7.3	32	.21	5.2	0.041	1.0	5.00	SPR	CG	N
0.360	9.14	B-45	.50	12.7	.276	7.0	35	6.1	.21	5.2	7.2	32	.29	7.5	0.042	1.1	6.00	SPR	C	Z
0.360	9.14	71138	.50	12.7	.276	7.0	47	8.3	.23	5.8	11	48	.21	5.3	0.042	1.1	5.00	MW	CG	N
0.360	9.14	71138S	.50	12.7	.276	7.0	40	7.0	.18	4.7	7.3	33	.21	5.3	0.042	1.1	5.00	SST	CG	N
0.360	9.14	L-70	.50	12.7	.270	6.9	56	9.9	.16	4.1	9.0	40	.23	5.7	0.045	1.1	5.00	SST	CG	N
0.360	9.14	71156	.50	12.7	.270	6.9	65	11	.20	5.2	13	59	.22	5.6	0.045	1.1	4.88	MW	CG	N
0.360	9.14	71156S	.50	12.7	.270	6.9	56	9.7	.16	4.1	9.0	40	.22	5.6	0.045	1.1	4.88	SST	CG	N
0.360	9.14	AA-96	.50	12.7	.266	6.8	66	12	.17	4.2	11	48	.26	6.6	0.047	1.2	5.50	SPR	CG	Z
0.360	9.14	71175	.50	12.7	.266	6.8	79	14	.19	4.9	15	67	.23	5.8	0.047	1.2	4.88	MW	CG	N
0.360	9.14	71175S	.50	12.7	.266	6.8	67	12	.15	3.9	10	45	.23	5.8	0.047	1.2	4.88	SST	CG	N
0.360	9.14	A13-16	.50	12.7	.266	6.8	77	13	.14	3.6	11	48	.24	6.0	0.047	1.2	5.00	SPR	CG	Z
0.360	9.14	71197	.50	12.7	.262	6.7	92	16	.18	4.7	17	76	.25	6.2	0.049	1.2	5.00	MW	CG	N
0.360	9.14	71197S	.50	12.7	.262	6.7	78	14	.15	3.7	12	51	.25	6.2	0.049	1.2	5.00	SST	CG	N
0.360	9.14	71219	.50	12.7	.258	6.6	108	19	.17	4.2	18	80	.26	6.5	0.051	1.3	5.00	MW	CG	N
0.360	9.14	71219S	.50	12.7	.258	6.6	92	16	.13	3.4	12	54	.26	6.5	0.051	1.3	5.00	SST	CG	N
0.360	9.14	71241	.50	12.7	.250	6.4	148	26	.15	3.8	22	99	.28	7.2	0.055	1.4	5.13	MW	CG	N
0.360	9.14	71241S	.50	12.7	.250	6.4	126	22	.12	3.1	15	67	.28	7.2	0.055	1.4	5.13	SST	CG	N
0.360	9.14	71263	.50	12.7	.242	6.1	201	35	.14	3.5	27	121	.30	7.7	0.059	1.5	5.13	MW	CG	N
0.360	9.14	71263S	.50	12.7	.242	6.1	171	30	.11	2.8	18	82	.30	7.7	0.059	1.5	5.13	SST	CG	N
0.360	9.14	3656	.50	12.7	.200	5.1	1084	190	.04	1.0	44	197	.36	9.1	0.080	2.0	4.50	SPR	CG	Z
0.360	9.14	B5-10	.53	13.5	.318	8.1	3.6	.63	.43	11	1.6	6.9	.08	2.1	0.021	0.5	4.00	MW	CG	N
0.360	9.14	M-82	.53	13.5	.300	7.6	7.3	1.3	.35	8.9	2.5	11	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.360	9.14	A13-20	.53	13.5	.294	7.5	15	2.5	.26	6.6	3.8	17	.17	4.2	0.033	0.8	5.00	SST	CG	N
0.360	9.14	A13-14	.53	13.5	.268	6.8	56	9.8	.17	4.4	9.6	43	.25	6.4	0.046	1.2	5.33	SST	CG	N
0.360	9.14	Y-14	.53	13.5	.264	6.7	113	20	.10	2.6	12	52	.20	5.2	0.048	1.2	4.25	SPR	CG	N
0.360	9.14	KK-89	.53	13.5	.260	6.6	101	18	.11	2.9	11	51	.25	6.4	0.050	1.3	5.00	SST	CG	N
0.360	9.14	12622	.53	13.5	.260	6.6	101	18	.12	3.1	12	54	.25	6.4	0.050	1.3	5.00	SPR	CG	N
0.360	9.14	S-26	.53	13.5	.258	6.6	74	13	.16	4.2	12	54	.36	9.1	0.051	1.3	6.00	SST	C	N
0.360	9.14	12646	.55	13.9	.294	7.5	9.4	1.6	.33	8.4	3.1	14	.22	5.5	0.033	0.8	6.50	SST	CG	N
0.360	9.14	71029	.56	14.2	.308	7.8	8.1	1.4	.34	8.7	2.8	12	.11	2.7	0.026	0.7	4.13	MW	CG	N
0.360	9.14	71029S	.56	14.2	.308	7.8	6.9	1.2	.27	6.8	1.9	8.3	.11	2.7	0.026	0.7	4.13	SST	CG	N
0.360	9.14	71048	.56	14.2	.302	7.7	11	1.9	.35	8.8	3.8	17	.13	3.3	0.029	0.7	4.50	MW	CG	N
0.360	9.14	71048S	.56	14.2	.302	7.7	9.4	1.6	.27	6.9	2.6	11	.13	3.3	0.029	0.7	4.50	SST	CG	N
0.360	9.14	71067	.56	14.2	.296	7.5	16	2.8	.32	8.1	5.1	23	.15	3.8	0.032	0.8	4.63	MW	CG	N
0.360	9.14	71067S	.56	14.2	.296	7.5	14	2.4	.25	6.3	3.4	15	.15	3.8	0.032	0.8	4.63	SST	CG	N
0.360	9.14	71085	.56	14.2	.290	7.4	21	3.7	.30	7.7	6.3	28	.18	4.4	0.035	0.9	5.00	MW	CG	N
0.360	9.14	71085S	.56	14.2	.290	7.4	18	3.1	.24	6.2	4.3	19	.18	4.4	0.035	0.9	5.00	SST	CG	N
0.360	9.14	71103	.56	14.2	.284	7.2	28	5.0	.28	7.2	8.1	36	.19	4.9	0.038	1.0	5.13	MW	CG	N
0.360	9.14	71103S	.56	14.2	.284	7.2	24	4.2	.23	5.8	5.5	24	.19	4.9	0.038	1.0	5.13	SST	CG	N
0.360	9.14	71121	.56	14.2	.280	7.1	34	5.9	.28	7.1	9.4	42	.22	5.5	0.040	1.0	5.38	MW	CG	N
0.360	9.14	71121S	.56	14.2	.280	7.1	29	5.0	.22	5.6	6.4	28	.22	5.5	0.040	1.0	5.38	SST	CG	N
0.360	9.14	71139	.56	14.2	.276	7.0	42	7.3	.26	6.6	11	48	.23	5.7	0.042	1.1	5.38	MW	CG	N
0.360	9.14	71139S	.56	14.2	.276	7.0	35	6.2	.21	5.3	7.3	33	.23	5.7	0.042	1.1	5.38	SST	CG	N
0.360	9.14	71157	.56	14.2	.270	6.9	56	9.7	.24	6.1	13	59	.24	6.1	0.045	1.1	5.38	MW	CG	N
0.360	9.14	71157S	.56	14.2	.270	6.9	47	8.3	.19	4.8	9.0	40	.24	6.1	0.045	1.1	5.38	SST	CG	N
0.360	9.14	71176	.56	14.2	.266	6.8	69	12	.22	5.6	15	67	.25	6.4	0.047	1.2	5.38	MW	CG	N
0.360	9.14	71176S	.56	14.2	.266	6.8	58	10	.17	4.4	10	45	.25	6.4	0.047	1.2	5.38	SST	CG	N
0.360	9.14	71198	.56	14.2	.262	6.7	80	14	.21	5.4	17	76	.26	6.7	0.049	1.2	5.38	MW	CG	N
0.360	9.14	71198S	.56	14.2	.262	6.7	68	12	.17	4.3	12	51	.26	6.7	0.049	1.2	5.38	SST	CG	N
0.360	9.14	71220	.56	14.2	.258	6.6	94	16	.19											



1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.360	9.14	B1-45	.63	15.9	.308	7.8	6.3	1.1	.29	7.5	1.9	8.3	.12	3.0	0.026	0.7	4.50	SST	CG	N
0.360	9.14	B12-28	.63	15.9	.308	7.8	7.1	1.2	.39	9.9	2.8	12	.12	3.0	0.026	0.7	4.50	MW	CG	N
0.360	9.14	FF-66	.63	15.9	.300	7.6	8.3	1.5	.34	8.7	2.8	13	.20	5.0	0.030	0.8	5.50	SST	C	N
0.360	9.14	10815	.63	15.9	.296	7.5	14	2.5	.26	6.5	3.7	16	.19	4.9	0.032	0.8	5.00	SPR	C	Z
0.360	9.14	3047	.63	15.9	.296	7.5	12	2.2	.42	11	5.1	23	.18	4.5	0.032	0.8	5.50	MW	CG	Z
0.360	9.14	4267	.63	15.9	.280	7.1	41	7.2	.16	4.2	6.8	30	.23	5.8	0.040	1.0	4.75	SPR	C	Z
0.360	9.14	GG-77	.63	15.9	.280	7.1	28	5.0	.24	6.1	6.8	30	.24	6.1	0.040	1.0	6.00	SPR	CG	N
0.360	9.14	L-99	.63	15.9	.280	7.1	18	3.1	.33	8.3	5.8	26	.30	7.6	0.040	1.0	7.50	SST	CG	N
0.360	9.14	K-65	.63	15.9	.280	7.1	15	2.7	.29	7.2	4.3	19	.34	8.6	0.040	1.0	8.50	SST	CG	N
0.360	9.14	S-1262	.63	15.9	.278	7.1	29	5.1	.23	5.9	6.8	30	.24	6.0	0.041	1.0	5.75	SST	CG	N
0.360	9.14	V-66	.63	15.9	.270	6.9	32	5.6	.27	6.7	8.4	37	.36	9.1	0.045	1.1	8.00	SPR	CG	N
0.360	9.14	A11-16	.63	15.9	.268	6.8	47	8.2	.21	5.2	9.6	43	.28	7.0	0.046	1.2	6.00	SST	CG	N
0.360	9.14	B7-4	.63	15.9	.268	6.8	49	8.6	.21	5.3	10	45	.29	7.3	0.046	1.2	6.25	SPR	CG	Z
0.360	9.14	10878	.63	15.9	.266	6.8	58	10	.19	4.8	11	48	.33	8.4	0.047	1.2	6.00	SPR	C	N
0.360	9.14	71030	.63	16.0	.308	7.8	7.2	1.3	.38	9.8	2.8	12	.12	3.0	0.026	0.7	4.50	MW	CG	N
0.360	9.14	71030S	.63	16.0	.308	7.8	6.1	1.1	.30	7.7	1.9	8.3	.12	3.0	0.026	0.7	4.50	SST	CG	N
0.360	9.14	71049	.63	16.0	.302	7.7	9.9	1.7	.39	9.8	3.8	17	.14	3.6	0.029	0.7	4.88	MW	CG	N
0.360	9.14	71049S	.63	16.0	.302	7.7	8.4	1.5	.30	7.7	2.6	11	.14	3.6	0.029	0.7	4.88	SST	CG	N
0.360	9.14	71068	.63	16.0	.296	7.5	15	2.6	.35	8.8	5.1	23	.16	4.0	0.032	0.8	4.88	MW	CG	N
0.360	9.14	71068S	.63	16.0	.296	7.5	12	2.2	.27	7.0	3.4	15	.16	4.0	0.032	0.8	4.88	SST	CG	N
0.360	9.14	71086	.63	16.0	.290	7.4	19	3.2	.34	8.7	6.3	28	.19	4.8	0.035	0.9	5.38	MW	CG	N
0.360	9.14	71086S	.63	16.0	.290	7.4	16	2.8	.27	6.9	4.3	19	.19	4.8	0.035	0.9	5.38	SST	CG	N
0.360	9.14	71104	.63	16.0	.284	7.2	25	4.4	.32	8.2	8.1	36	.21	5.4	0.038	1.0	5.63	MW	CG	N
0.360	9.14	71104S	.63	16.0	.284	7.2	21	3.7	.26	6.6	5.5	24	.21	5.4	0.038	1.0	5.63	SST	CG	N
0.360	9.14	71122	.63	16.0	.280	7.1	30	5.2	.32	8.1	9.4	42	.23	5.8	0.040	1.0	5.75	MW	CG	N
0.360	9.14	71122S	.63	16.0	.280	7.1	25	4.4	.25	6.4	6.4	28	.23	5.8	0.040	1.0	5.75	SST	CG	N
0.360	9.14	71140	.63	16.0	.276	7.0	38	6.6	.29	7.3	11	48	.24	6.0	0.042	1.1	5.63	MW	CG	N
0.360	9.14	71140S	.63	16.0	.276	7.0	32	5.6	.23	5.8	7.3	33	.24	6.0	0.042	1.1	5.63	SST	CG	N
0.360	9.14	71158	.63	16.0	.270	6.9	49	8.6	.27	6.9	13	59	.26	6.7	0.045	1.1	5.88	MW	CG	N
0.360	9.14	71158S	.63	16.0	.270	6.9	42	7.3	.22	5.5	9.0	40	.26	6.7	0.045	1.1	5.88	SST	CG	N
0.360	9.14	71177	.63	16.0	.266	6.8	61	11	.25	6.3	15	67	.27	6.9	0.047	1.2	5.75	MW	CG	N
0.360	9.14	71177S	.63	16.0	.266	6.8	52	9.1	.20	5.0	10	45	.27	6.9	0.047	1.2	5.75	SST	CG	N
0.360	9.14	71199	.63	16.0	.262	6.7	71	12	.24	6.1	17	76	.29	7.3	0.049	1.2	5.88	MW	CG	N
0.360	9.14	71199S	.63	16.0	.262	6.7	60	11	.19	4.9	12	51	.29	7.3	0.049	1.2	5.88	SST	CG	N
0.360	9.14	71221	.63	16.0	.258	6.6	83	14	.22	5.5	18	80	.31	7.8	0.051	1.3	6.00	MW	CG	N
0.360	9.14	71221S	.63	16.0	.258	6.6	70	12	.17	4.4	12	54	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.360	9.14	71243	.63	16.0	.250	6.4	113	20	.20	5.0	22	99	.34	8.6	0.055	1.4	6.13	MW	CG	N
0.360	9.14	71243S	.63	16.0	.250	6.4	96	17	.16	4.0	15	67	.34	8.6	0.055	1.4	6.13	SST	CG	N
0.360	9.14	71265	.63	16.0	.242	6.1	153	27	.18	4.5	27	121	.36	9.2	0.059	1.5	6.13	MW	CG	N
0.360	9.14	71265S	.63	16.0	.242	6.1	130	23	.14	3.6	18	82	.36	9.2	0.059	1.5	6.13	SST	CG	N
0.360	9.14	JJ-53	.66	16.7	.284	7.2	23	4.0	.26	6.5	5.8	26	.23	5.8	0.038	1.0	6.00	SPR	CG	N
0.360	9.14	10954	.66	16.7	.266	6.8	42	7.4	.26	6.5	11	48	.40	10.2	0.047	1.2	7.50	SPR	C	N
0.360	9.14	12695	.67	17.1	.236	6.0	134	23	.18	4.5	24	105	.50	12.6	0.062	1.6	8.00	MW	CG	N
0.360	9.14	B5-16	.69	17.4	.314	8.0	4.2	.74	.48	12	2.0	9.1	.13	3.2	0.023	0.6	4.50	MW	C	N
0.360	9.14	B4-8	.69	17.4	.312	7.9	1.3	.22	.38	9.5	.47	2.1	.31	7.9	0.024	0.6	12.0	MW	C	Z
0.360	9.14	J-25	.69	17.4	.310	7.9	5.5	.96	.45	11	2.5	11	.14	3.7	0.025	0.6	4.75	MW	C	Z
0.360	9.14	W-45	.69	17.4	.280	7.1	20	3.5	.32	8.2	6.4	28	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.360	9.14	A13-11	.69	17.4	.274	7.0	32	5.6	.25	6.3	7.9	35	.27	6.9	0.043	1.1	6.25	SST	CG	N
0.360	9.14	N-68	.69	17.4	.270	6.9	24	4.2	.24	6.0	5.7	25	.45	11.4	0.045	1.1	9.00	SST	C	N
0.360	9.14	3668	.69	17.4	.268	6.8	52	9.2	.19	5.0	10	45	.32	8.2	0.046	1.2	6.00	SPR	C	Z
0.360	9.14	BB-79	.69	17.4	.250	6.4	66	11.6	.190	4.83	12.5	55.6	.50	12.7	0.055	1.4	9.00	SPR	CG	N
0.360	9.14	00-37	.69	17.4	.240	6.1	100	17	.15	3.7	15	65	.54	13.7	0.060	1.5	9.00	SPR	CG	N
0.360	9.14	71031	.69	17.5	.308	7.8	6.6	1.2	.42	11	2.8	12	.12	3.1	0.026	0.7	4.63	MW	CG	N
0.360	9.14	71031S	.69	17.5	.308	7.8	5.6	.98	.33	8.4	1.9	8.3	.12	3.1	0.026	0.7	4.63	SST	CG	N
0.360	9.14	71050	.69	17.5	.302	7.7	8.6	1.5	.45	11	3.8	17	.15	3.9	0.029	0.7	5.25	MW	CG	N
0.360	9.14	71050S	.69	17.5	.302	7.7	7.3	1.3	.35	8.9	2.6	11	.15	3.9	0.029	0.7	5.25	SST	CG	N
0.360	9.14	71069	.69	17.5	.296	7.5	13	2.3	.40	10	5.1	23	.17	4.3	0.032	0.8	5.25	MW	CG	N
0.360	9.14	71069S	.69	17.5	.296	7.5	11	1.9	.31	7.9	3.4	15	.17	4.3	0.032	0.8	5.25	SST	CG	N
0.360	9.14	71087	.69	17.5	.290	7.4	16	2.9	.39	9.8	6.3	28	.21	5.2	0.035	0.9	5.88	MW	CG	N
0.360	9.14	71087S	.69	17.5	.290	7.4	14	2.4	.31	7.8	4.3	19	.21	5.2	0.035	0.9	5.88	SST	CG	N
0.360	9.14	71105	.69	17.5	.284	7.2	22	3.9	.37	9.3	8.1	36	.23	5.9	0.038	1.0	6.13	MW	CG	N
0.360	9.14	71105S	.69	17.5	.284	7.2	19	3.3	.29	7.4	5.5	24	.23	5.9	0.038	1.0	6.13	SST	CG	N
0.360	9.14	71123	.69	17.5	.280	7.1	27	4.7	.35	9.0	9.4	42	.25	6.4	0.040	1.0	6.25	MW	CG	N
0.360	9.14	71123S	.69	17.5	.280	7.1	23	4.0	.28	7.1	6.4	28	.25	6.4	0.040	1.0	6.25	SST	CG	N
0.360	9.14	71141	.69	17.5	.276	7.0	34	5.9	.32	8.2	11	48	.26	6.5	0.042	1.1	6.13	MW	CG	N
0.360	9.14	71141S	.69	17.5	.276	7.0	28	5.0	.26	6.5	7.3	33	.26	6.5	0.042	1.1	6.13	SST	CG	N
0.360	9.14	71159	.69	17.5	.270	6.9	44	7.7	.30	7.7	13	59	.28	7.1	0.045	1.1	6.25	MW	CG	N
0.360	9.14	71159S	.69	17.5	.270	6.9	37	6.5	.24	6.1	9.0	40	.28	7.1	0.045	1.1	6.25	SST	CG	N
0.360	9.14	71178	.69	17.5	.266	6.8	54	9.4	.28											




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.360	9.14	B7-54	.72	18.2	.268	6.8	49	8.6	.21	5.3	10	45	.33	8.5	0.046	1.2	6.25	SPR	C	N
0.360	9.14	3596	.72	18.2	.210	5.3	331	58	.11	2.8	37	164	.60	15.2	0.075	1.9	8.00	SPR	CG	Z
0.360	9.14	B12-18	.75	19.1	.316	8.0	2.9	.51	.61	15	1.8	8.0	.11	2.8	0.022	0.6	5.00	MW	CG	N
0.360	9.14	M-110	.75	19.1	.310	7.9	5.0	.88	.49	12	2.5	11	.15	3.8	0.025	0.6	5.00	MW	C	GI
0.360	9.14	71032	.75	19.1	.308	7.8	6.1	1.1	.46	12	2.8	12	.13	3.2	0.026	0.7	4.88	MW	CG	N
0.360	9.14	71032S	.75	19.1	.308	7.8	5.1	.90	.36	9.2	1.9	8.3	.13	3.2	0.026	0.7	4.88	SST	CG	N
0.360	9.14	B12-22	.75	19.1	.306	7.8	6.4	1.1	.48	12	3.1	14	.14	3.6	0.027	0.7	5.25	MW	CG	GI
0.360	9.14	71051	.75	19.1	.302	7.7	7.9	1.4	.48	12	3.8	17	.16	4.1	0.029	0.7	5.50	MW	CG	N
0.360	9.14	71051S	.75	19.1	.302	7.7	6.7	1.2	.38	9.7	2.6	11	.16	4.1	0.029	0.7	5.50	SST	CG	N
0.360	9.14	CC-50	.75	19.1	.300	7.6	7.1	1.2	.40	10	2.8	13	.21	5.3	0.030	0.8	6.00	SST	C	N
0.360	9.14	BB-71	.75	19.1	.300	7.6	3.6	.63	.45	11	1.6	7.3	.30	7.6	0.030	0.8	10.0	SST	CG	N
0.360	9.14	10014	.75	19.1	.296	7.5	11	1.9	.48	12	5.1	23	.19	4.9	0.032	0.8	6.00	MW	C	Z
0.360	9.14	71070	.75	19.1	.296	7.5	12	2.1	.43	11	5.1	23	.18	4.6	0.032	0.8	5.63	MW	CG	N
0.360	9.14	71070S	.75	19.1	.296	7.5	10	1.8	.34	8.6	3.4	15	.18	4.6	0.032	0.8	5.63	SST	CG	N
0.360	9.14	71088	.75	19.1	.290	7.4	15	2.6	.42	11	6.3	28	.21	5.4	0.035	0.9	6.13	MW	CG	N
0.360	9.14	71088S	.75	19.1	.290	7.4	13	2.2	.34	8.5	4.3	19	.21	5.4	0.035	0.9	6.13	SST	CG	N
0.360	9.14	B3-35	.75	19.1	.290	7.4	14	2.4	.45	12	6.3	28	.23	5.8	0.035	0.9	6.50	MW	CG	N
0.360	9.14	71106	.75	19.1	.284	7.2	21	3.7	.39	9.8	8.1	36	.24	6.0	0.038	1.0	6.25	MW	CG	N
0.360	9.14	71106S	.75	19.1	.284	7.2	18	3.1	.31	7.8	5.5	24	.24	6.0	0.038	1.0	6.25	SST	CG	N
0.360	9.14	S-1158	.75	19.1	.280	7.1	20	3.5	.32	8.2	6.4	28	.32	8.1	0.040	1.0	7.00	SST	C	N
0.360	9.14	71124	.75	19.1	.280	7.1	24	4.3	.39	9.8	9.4	42	.27	6.7	0.040	1.0	6.63	MW	CG	N
0.360	9.14	71124S	.75	19.1	.280	7.1	21	3.6	.31	7.8	6.4	28	.27	6.7	0.040	1.0	6.63	SST	CG	N
0.360	9.14	3785	.75	19.1	.276	7.0	28	4.9	.28	7.1	7.8	35	.34	8.5	0.042	1.1	7.00	SPR	C	Z
0.360	9.14	71142	.75	19.1	.276	7.0	31	5.4	.35	8.9	11	48	.27	6.9	0.042	1.1	6.50	MW	CG	N
0.360	9.14	71142S	.75	19.1	.276	7.0	26	4.6	.28	7.1	7.3	33	.27	6.9	0.042	1.1	6.50	SST	CG	N
0.360	9.14	A14-44	.75	19.1	.274	7.0	33	5.7	.26	6.5	8.4	37	.29	7.4	0.043	1.1	6.75	SPR	CG	Z
0.360	9.14	10027	.75	19.1	.270	6.9	38	6.7	.25	6.4	9.6	43	.32	8.0	0.045	1.1	7.00	SPR	CG	Z
0.360	9.14	G-22	.75	19.1	.270	6.9	18	3.2	.26	6.5	4.7	21	.50	12.6	0.045	1.1	11.0	SST	CG	N
0.360	9.14	H-29	.75	19.1	.270	6.9	33	5.8	.27	6.9	9.0	40	.32	8.0	0.045	1.1	7.00	SST	CG	N
0.360	9.14	71160	.75	19.1	.270	6.9	40	7.0	.33	8.5	13	59	.30	7.7	0.045	1.1	6.75	MW	CG	N
0.360	9.14	71160S	.75	19.1	.270	6.9	34	5.9	.27	6.8	9.0	40	.30	7.7	0.045	1.1	6.75	SST	CG	N
0.360	9.14	71179	.75	19.1	.266	6.8	39	6.9	.38	9.6	15	66	.37	9.4	0.047	1.2	7.88	MW	CG	N
0.360	9.14	71179S	.75	19.1	.266	6.8	33	5.8	.31	7.8	10	45	.37	9.4	0.047	1.2	7.88	SST	CG	N
0.360	9.14	AA-94	.75	19.1	.266	6.8	33	5.9	.30	7.7	10	45	.38	9.6	0.047	1.2	8.00	SST	CG	N
0.360	9.14	71201	.75	19.1	.262	6.7	57	10	.30	7.6	17	76	.34	8.6	0.049	1.2	6.88	MW	CG	N
0.360	9.14	71201S	.75	19.1	.262	6.7	48	8.5	.24	6.0	12	51	.34	8.6	0.049	1.2	6.88	SST	CG	N
0.360	9.14	2612	.75	19.1	.260	6.6	51	8.9	.24	6.1	12	54	.40	10.2	0.050	1.3	8.00	SPR	CG	Z
0.360	9.14	71223	.75	19.1	.258	6.6	66	12	.27	6.9	18	80	.36	9.1	0.051	1.3	7.00	MW	CG	N
0.360	9.14	71223S	.75	19.1	.258	6.6	56	9.8	.22	5.5	12	54	.36	9.1	0.051	1.3	7.00	SST	CG	N
0.360	9.14	DD-100	.75	19.1	.252	6.4	68	12	.21	5.3	14	64	.41	10.3	0.054	1.4	7.50	SST	CG	N
0.360	9.14	71245	.75	19.1	.250	6.4	90	16	.25	6.3	22	99	.39	10.0	0.055	1.4	7.13	MW	CG	N
0.360	9.14	71245S	.75	19.1	.250	6.4	77	13	.20	5.0	15	67	.39	10.0	0.055	1.4	7.13	SST	CG	N
0.360	9.14	M-107	.75	19.1	.242	6.1	117	21	.17	4.3	20	87	.44	11.2	0.059	1.5	7.50	SPR	CG	Z
0.360	9.14	71267	.75	19.1	.242	6.1	121	21	.22	5.7	27	121	.43	10.9	0.059	1.5	7.25	MW	CG	N
0.360	9.14	71267S	.75	19.1	.242	6.1	103	18	.18	4.6	18	82	.43	10.9	0.059	1.5	7.25	SST	CG	N
0.360	9.14	BB-52	.78	19.8	.300	7.6	9.7	1.7	.29	7.4	2.8	13	.15	3.8	0.030	0.8	5.00	SST	CG	N
0.360	9.14	B-85	.78	19.8	.298	7.6	8.3	1.5	.37	9.5	3.1	14	.22	5.5	0.031	0.8	6.00	SST	C	N
0.360	9.14	A13-17	.78	19.8	.292	7.4	14	2.4	.44	11	6.1	27	.20	5.2	0.034	0.9	6.00	MW	CG	N
0.360	9.14	S-1533	.78	19.8	.290	7.4	10	1.8	.43	11	4.3	19	.26	6.7	0.035	0.9	7.50	SST	CG	N
0.360	9.14	KK-49	.78	19.8	.260	6.6	51	8.9	.24	6.1	12	54	.40	10.2	0.050	1.3	8.00	SPR	CG	N
0.360	9.14	10447	.78	19.8	.258	6.6	67	12	.19	4.9	13	57	.41	10.4	0.051	1.3	7.00	SPR	C	Z
0.360	9.14	71033	.81	20.6	.308	7.8	5.6	.98	.49	13	2.8	12	.13	3.4	0.026	0.7	5.13	MW	CG	N
0.360	9.14	71033S	.81	20.6	.308	7.8	4.8	.83	.39	9.9	1.9	8.3	.13	3.4	0.026	0.7	5.13	SST	CG	N
0.360	9.14	71052	.81	20.6	.302	7.7	7.3	1.3	.52	13	3.8	17	.17	4.3	0.029	0.7	5.88	MW	CG	N
0.360	9.14	71052S	.81	20.6	.302	7.7	6.2	1.1	.41	10	2.6	11	.17	4.3	0.029	0.7	5.88	SST	CG	N
0.360	9.14	71071	.81	20.6	.296	7.5	11	1.9	.46	12	5.1	23	.19	4.8	0.032	0.8	5.88	MW	CG	N
0.360	9.14	71071S	.81	20.6	.296	7.5	9.4	1.7	.36	9.2	3.4	15	.19	4.8	0.032	0.8	5.88	SST	CG	N
0.360	9.14	71089	.81	20.6	.290	7.4	14	2.4	.46	12	6.3	28	.23	5.9	0.035	0.9	6.63	MW	CG	N
0.360	9.14	71089S	.																	




1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.360	9.14	A13-26	.81	20.6	.294	7.5	10	1.8	.37	9.3	3.8	17	.21	5.2	0.033	0.8	6.25	SST	CG	N
0.360	9.14	H-64	.81	20.6	.290	7.4	12	2.0	.40	10	4.6	20	.26	6.7	0.035	0.9	7.50	SPR	CG	Z
0.360	9.14	4238	.81	20.6	.288	7.3	18	3.1	.28	7.1	5.0	22	.25	6.4	0.036	0.9	6.00	SPR	CG	Z
0.360	9.14	B1-15	.81	20.6	.266	6.8	44	7.7	.25	6.3	11	48	.34	8.7	0.047	1.2	7.25	SPR	CG	GI
0.360	9.14	MM-48	.84	21.4	.304	7.7	6.1	1.1	.57	14	3.5	15	.20	5.0	0.028	0.7	6.00	MW	C	N
0.360	9.14	N-3	.84	21.4	.226	5.7	172	30	.15	3.9	27	118	.54	13.6	0.067	1.7	8.00	SST	CG	N
0.360	9.14	4279	.88	22.2	.310	7.9	4.3	.75	.57	15	2.5	11	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.360	9.14	S-1279	.88	22.2	.310	7.9	3.3	.57	.50	13	1.7	7.3	.15	3.8	0.025	0.6	6.00	SST	CG	N
0.360	9.14	Z-55	.88	22.2	.310	7.9	3.7	.66	.44	11	1.7	7.3	.16	4.1	0.025	0.6	5.50	SST	C	N
0.360	9.14	XX-69	.88	22.2	.306	7.8	5.6	.97	.56	14	3.1	14	.18	4.6	0.027	0.7	5.75	MW	C	Z
0.360	9.14	J-11	.88	22.2	.302	7.7	4.0	.71	.59	15	2.4	11	.29	7.4	0.029	0.7	9.00	MW	C	Z
0.360	9.14	B17-133	.88	22.2	.300	7.6	5.9	1.0	.65	17	3.9	17	.23	5.7	0.030	0.8	7.50	MW	CG	Z
0.360	9.14	W-19	.88	22.2	.296	7.5	7.5	1.3	.46	12	3.4	15	.22	5.7	0.032	0.8	7.00	SST	CG	N
0.360	9.14	10095	.88	22.2	.294	7.5	9.8	1.7	.41	10	4.0	18	.26	6.7	0.033	0.8	7.00	SPR	C	Z
0.360	9.14	A13-49	.88	22.2	.294	7.5	11	1.9	.37	9.4	4.0	18	.21	5.4	0.033	0.8	6.50	SPR	CG	GI
0.360	9.14	O-93	.88	22.2	.290	7.4	16	2.8	.29	7.3	4.6	20	.21	5.3	0.035	0.9	6.00	SPR	C	GI
0.360	9.14	QQ-68	.88	22.2	.282	7.2	13	2.3	.45	11	5.9	26	.38	9.7	0.039	1.0	8.75	SST	C	N
0.360	9.14	GG-10	.88	22.2	.280	7.1	13	2.2	.48	12	6.0	27	.40	10.2	0.040	1.0	10.0	SST	CG	N
0.360	9.14	S-1257	.88	22.2	.278	7.1	19	3.3	.36	9.1	6.8	30	.32	8.1	0.041	1.0	7.75	SST	CG	N
0.360	9.14	A11-25	.88	22.2	.268	6.8	31	5.4	.31	7.8	9.6	43	.37	9.3	0.046	1.2	8.00	SST	CG	N
0.360	9.14	W-44	.88	22.2	.266	6.8	37	6.4	.28	7.1	10	45	.35	9.0	0.047	1.2	7.50	SST	CG	N
0.360	9.14	H-22	.88	22.2	.252	6.4	50	8.7	.29	7.3	14	64	.51	13.0	0.054	1.4	9.50	SST	CG	N
0.360	9.14	L-82	.88	22.2	.252	6.4	51	8.9	.30	7.6	15	68	.57	14.4	0.054	1.4	10.5	SPR	CG	Z
0.360	9.14	O-34	.88	22.2	.230	5.8	149	26	.16	4.2	24	109	.52	13.2	0.065	1.7	8.00	SST	CG	N
0.360	9.14	71034	.88	22.4	.308	7.8	5.0	.87	.56	14	2.8	12	.15	3.7	0.026	0.7	5.63	MW	CG	N
0.360	9.14	71034S	.88	22.4	.308	7.8	4.2	.74	.44	11	1.9	8.3	.15	3.7	0.026	0.7	5.63	SST	CG	N
0.360	9.14	71053	.88	22.4	.302	7.7	6.7	1.2	.57	15	3.8	17	.18	4.5	0.029	0.7	6.13	MW	CG	N
0.360	9.14	71053S	.88	22.4	.302	7.7	5.7	1.0	.45	11	2.6	11	.18	4.5	0.029	0.7	6.13	SST	CG	N
0.360	9.14	71072	.88	22.4	.296	7.5	10	1.7	.51	13	5.1	23	.20	5.1	0.032	0.8	6.25	MW	CG	N
0.360	9.14	71072S	.88	22.4	.296	7.5	8.5	1.5	.41	10	3.4	15	.20	5.1	0.032	0.8	6.25	SST	CG	N
0.360	9.14	71090	.88	22.4	.290	7.4	13	2.2	.50	13	6.3	28	.24	6.1	0.035	0.9	6.88	MW	CG	N
0.360	9.14	71090S	.88	22.4	.290	7.4	11	1.9	.40	10	4.3	19	.24	6.1	0.035	0.9	6.88	SST	CG	N
0.360	9.14	71108	.88	22.4	.284	7.2	17	3.0	.48	12	8.1	36	.28	7.0	0.038	1.0	7.25	MW	CG	N
0.360	9.14	71108S	.88	22.4	.284	7.2	14	2.5	.38	9.6	5.5	24	.28	7.0	0.038	1.0	7.25	SST	CG	N
0.360	9.14	71126	.88	22.4	.280	7.1	20	3.6	.46	12	9.4	42	.30	7.6	0.040	1.0	7.50	MW	CG	N
0.360	9.14	71126S	.88	22.4	.280	7.1	17	3.0	.37	9.3	6.4	28	.30	7.6	0.040	1.0	7.50	SST	CG	N
0.360	9.14	71144	.88	22.4	.276	7.0	25	4.4	.43	11	11	48	.32	8.0	0.042	1.1	7.50	MW	CG	N
0.360	9.14	71144S	.88	22.4	.276	7.0	21	3.7	.34	8.7	7.3	33	.32	8.0	0.042	1.1	7.50	SST	CG	N
0.360	9.14	71162	.88	22.4	.270	6.9	33	5.8	.40	10	13	59	.35	8.9	0.045	1.1	7.75	MW	CG	N
0.360	9.14	71162S	.88	22.4	.270	6.9	28	4.9	.32	8.2	9.0	40	.35	8.9	0.045	1.1	7.75	SST	CG	N
0.360	9.14	71181	.88	22.4	.266	6.8	33	5.7	.46	12	15	66	.42	10.7	0.047	1.2	9.00	MW	CG	N
0.360	9.14	71181S	.88	22.4	.266	6.8	28	4.9	.37	9.3	10	45	.42	10.7	0.047	1.2	9.00	SST	CG	N
0.360	9.14	71203	.88	22.4	.262	6.7	48	8.3	.36	9.1	17	76	.38	9.6	0.049	1.2	7.75	MW	CG	N
0.360	9.14	71203S	.88	22.4	.262	6.7	41	7.1	.28	7.2	12	51	.38	9.6	0.049	1.2	7.75	SST	CG	N
0.360	9.14	71225	.88	22.4	.258	6.6	55	9.6	.32	8.3	18	80	.41	10.4	0.051	1.3	8.00	MW	CG	N
0.360	9.14	71225S	.88	22.4	.258	6.6	47	8.2	.26	6.6	12	54	.41	10.4	0.051	1.3	8.00	SST	CG	N
0.360	9.14	71247	.88	22.4	.250	6.4	75	13	.30	7.5	22	99	.45	11.4	0.055	1.4	8.13	MW	CG	N
0.360	9.14	71247S	.88	22.4	.250	6.4	64	11	.24	6.0	15	67	.45	11.4	0.055	1.4	8.13	SST	CG	N
0.360	9.14	71269	.88	22.4	.242	6.1	101	18	.27	6.9	27	121	.49	12.6	0.059	1.5	8.38	MW	CG	N
0.360	9.14	71269S	.88	22.4	.242	6.1	86	15	.22	5.5	18	82	.49	12.6	0.059	1.5	8.38	SST	CG	N
0.360	9.14	Y-24	.91	23.0	.290	7.4	9.1	1.6	.51	13	4.6	20	.32	8.0	0.035	0.9	9.00	SPR	CG	N
0.360	9.14	B2-14	.93	23.7	.258	6.6	6.3	1.1	.40	10	2.5	11	.54	13.6	0.051	1.3	9.50	MW	C	Z
0.360	9.14	M-133	.94	23.8	.330	8.4	.22	.04	.79	20	.17	.78	.15	3.8	0.015	0.4	9.00	SST	C	N
0.360	9.14	JJ-82	.94	23.8	.316	8.0	2.2	.39	.78	20	1.7	7.7	.15	3.9	0.022	0.6	6.00	MW	C	N
0.360	9.14	1929	.94	23.8	.310	7.9	3.9	.68	.63	16	2.5	11	.17	4.4	0.025	0.6	5.88	MW	C	Z
0.360	9.14	F-59	.94	23.8	.308	7.8	4.4	.78	.62	16	2.8	12	.18	4.6	0.026	0.7	6.00	MW	C	Z
0.360	9.14	A9-59	.94	23.8	.302	7.7	5.7	.99	.68	17	3.8	17	.20	5.2	0.029	0.7	7.00	MW	CG	N
0.360	9.14	S-179	.94	23.8	.298	7.6	5.6	.97	.56	14	3.1	14	.28	7.1	0.031	0.8	8.00	SST	C	N
0.360	9.14	KK-87	.94	23.8	.296	7.5	7.8	1.4	.65	17	5.1	23	.27	6.9	0.032	0.8	7.50	MW	C	N
0.360	9.14	F-60	.94	23.8	.270	6.9	32	5.6	.42	11	13	59	.41	10.3	0.045	1.1	8.00	MW	C	Z
0.360	9.14	S-373	.94	23.8	.150	3.8	1576	276	.05	1.3	81	361	.84	21.3	0.105	2.7	8.00	SST	CG	N
0.360	9.14	71035	.94	23.9	.308	7.8	4.6	.80	.61	15	2.8	12	.15	3.9	0.026	0.7	5.88	MW	CG	N
0.360	9.14	71035S	.94	23.9	.308	7.8	3.9	.68	.48	12	1.9	8.3	.15	3.9	0.026	0.7	5.88	SST	CG	N
0.360	9.14	71054	.94	23.9	.302	7.7	6.1	1.1	.63	16	3.8	17	.19	4.9	0.029	0.7	6.63	MW	CG	N
0.360	9.14	71054S	.94	23.9	.302	7.7	5.2	.91	.49	13	2.6	11	.19	4.9	0.029	0.7	6.63	SST	CG	N
0.360	9.14	71073	.94	23.9	.296	7.5	9.5	1.7	.54	14	5.1	23	.21	5.3	0.032	0.8	6.50	MW	CG	N
0.360	9.14	71073S	.94	23.9	.296	7.5	8.0	1.4	.43	11	3.4	15	.21	5.3	0.032	0.8	6.50	SST	CG	N
0.360	9.14	71091	.94	23.9	.290	7.4	12	2.1	.53	14	6.3	28	.25	6.4	0.035	0.9	7.25	MW	CG	N
0.360	9.14	71091S	.94	23.9	.290	7.4	10	1.8	.42	11	4.3	19	.25	6.4	0.035	0				




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.360	9.14	71075	1.13	28.7	.296	7.5	7.5	1.3	.68	17	5.1	23	.25	6.3	0.032	0.8	7.75	MW	CG	N
0.360	9.14	71075S	1.13	28.7	.296	7.5	6.4	1.1	.54	14	3.4	15	.25	6.3	0.032	0.8	7.75	SST	CG	N
0.360	9.14	71093	1.13	28.7	.290	7.4	9.8	1.7	.65	17	6.3	28	.30	7.6	0.035	0.9	8.50	MW	CG	N
0.360	9.14	71093S	1.13	28.7	.290	7.4	8.3	1.5	.52	13	4.3	19	.30	7.6	0.035	0.9	8.50	SST	CG	N
0.360	9.14	71111	1.13	28.7	.284	7.2	13	2.3	.62	16	8.1	36	.34	8.6	0.038	1.0	8.88	MW	CG	N
0.360	9.14	71111S	1.13	28.7	.284	7.2	11	1.9	.50	13	5.5	24	.34	8.6	0.038	1.0	8.88	SST	CG	N
0.360	9.14	71129	1.13	28.7	.280	7.1	16	2.7	.60	15	9.4	42	.37	9.3	0.040	1.0	9.13	MW	CG	N
0.360	9.14	71129S	1.13	28.7	.280	7.1	13	2.3	.48	12	6.4	28	.37	9.3	0.040	1.0	9.13	SST	CG	N
0.360	9.14	71147	1.13	28.7	.276	7.0	19	3.3	.58	15	11	48	.39	10.0	0.042	1.1	9.38	MW	CG	N
0.360	9.14	71147S	1.13	28.7	.276	7.0	16	2.8	.46	12	7.3	33	.39	10.0	0.042	1.1	9.38	SST	CG	N
0.360	9.14	71165	1.13	28.7	.270	6.9	25	4.3	.54	14	13	59	.43	11.0	0.045	1.1	9.63	MW	CG	N
0.360	9.14	71165S	1.13	28.7	.270	6.9	21	3.7	.43	11	9.0	40	.43	11.0	0.045	1.1	9.63	SST	CG	N
0.360	9.14	71184	1.13	28.7	.266	6.8	31	5.5	.48	12	15	67	.44	11.2	0.047	1.2	9.38	MW	CG	N
0.360	9.14	71184S	1.13	28.7	.266	6.8	27	4.6	.38	9.8	10	45	.44	11.2	0.047	1.2	9.38	SST	CG	N
0.360	9.14	71206	1.13	28.7	.262	6.7	36	6.3	.47	12	17	76	.47	12.0	0.049	1.2	9.63	MW	CG	N
0.360	9.14	71206S	1.13	28.7	.262	6.7	31	5.4	.37	9.5	12	51	.47	12.0	0.049	1.2	9.63	SST	CG	N
0.360	9.14	71228	1.13	28.7	.258	6.6	42	7.4	.43	11	18	80	.50	12.8	0.051	1.3	9.88	MW	CG	N
0.360	9.14	71228S	1.13	28.7	.258	6.6	36	6.3	.34	8.6	12	54	.50	12.8	0.051	1.3	9.88	SST	CG	N
0.360	9.14	71250	1.13	28.7	.250	6.4	57	10	.39	9.9	22	99	.56	14.1	0.055	1.4	10.1	MW	CG	N
0.360	9.14	71250S	1.13	28.7	.250	6.4	48	8.5	.31	7.9	15	67	.56	14.1	0.055	1.4	10.1	SST	CG	N
0.360	9.14	71271	1.13	28.7	.242	6.1	77	13	.36	9.1	27	121	.61	15.5	0.059	1.5	10.4	MW	CG	N
0.360	9.14	71271S	1.13	28.7	.242	6.1	65	11	.28	7.2	18	82	.61	15.5	0.059	1.5	10.4	SST	CG	N
0.360	9.14	PP-77	1.16	29.4	.300	7.6	4.7	.83	.60	15	2.8	13	.24	6.1	0.030	0.8	8.00	SST	CG	N
0.360	9.14	F-35	1.19	30.2	.308	7.8	3.6	.62	.78	20	2.8	12	.21	5.3	0.026	0.7	7.00	MW	C	Z
0.360	9.14	YY-43	1.19	30.2	.292	7.4	5.1	.89	.71	18	3.6	16	.48	12.1	0.034	0.9	13.0	SPR	C	Z
0.360	9.14	3664	1.19	30.2	.270	6.9	15	2.6	.47	12	6.9	30	.72	18.3	0.045	1.1	15.0	SPR	C	Z
0.360	9.14	71038	1.25	31.8	.308	7.8	3.3	.57	.85	22	2.8	12	.19	4.9	0.026	0.7	7.38	MW	CG	N
0.360	9.14	71038S	1.25	31.8	.308	7.8	2.8	.48	.67	17	1.9	8.3	.19	4.9	0.026	0.7	7.38	SST	CG	N
0.360	9.14	S-1272	1.25	31.8	.302	7.7	4.5	.78	.57	15	2.6	11	.25	6.3	0.029	0.7	7.50	SST	C	N
0.360	9.14	71057	1.25	31.8	.302	7.7	4.6	.81	.83	21	3.8	17	.24	6.0	0.029	0.7	8.13	MW	CG	N
0.360	9.14	71057S	1.25	31.8	.302	7.7	3.9	.68	.66	17	2.6	11	.24	6.0	0.029	0.7	8.13	SST	CG	N
0.360	9.14	NN-46	1.25	31.8	.300	7.6	5.8	1.0	.49	12	2.8	13	.21	5.3	0.030	0.8	7.00	SST	CG	N
0.360	9.14	71076	1.25	31.8	.296	7.5	6.8	1.2	.75	19	5.1	23	.26	6.7	0.032	0.8	8.25	MW	CG	N
0.360	9.14	71076S	1.25	31.8	.296	7.5	5.8	1.0	.59	15	3.4	15	.26	6.7	0.032	0.8	8.25	SST	CG	N
0.360	9.14	12502	1.25	31.8	.292	7.4	8.0	1.4	.51	13	4.1	18	.31	7.8	0.034	0.9	8.00	SST	C	N
0.360	9.14	71094	1.25	31.8	.290	7.4	8.8	1.5	.73	18	6.3	28	.32	8.1	0.035	0.9	9.13	MW	CG	N
0.360	9.14	71094S	1.25	31.8	.290	7.4	7.4	1.3	.58	15	4.3	19	.32	8.1	0.035	0.9	9.13	SST	CG	N
0.360	9.14	S-1281	1.25	31.8	.286	7.3	9.4	1.6	.54	14	5.1	23	.35	8.9	0.037	0.9	9.50	SST	CG	N
0.360	9.14	TT-38	1.25	31.8	.284	7.2	9.1	1.6	.64	16	5.8	26	.49	12.5	0.038	1.0	12.0	SPR	C	Z
0.360	9.14	71112	1.25	31.8	.284	7.2	12	2.1	.68	17	8.1	36	.37	9.3	0.038	1.0	9.63	MW	CG	N
0.360	9.14	71112S	1.25	31.8	.284	7.2	10	1.8	.54	14	5.5	24	.37	9.3	0.038	1.0	9.63	SST	CG	N
0.360	9.14	71130	1.25	31.8	.280	7.1	14	2.4	.67	17	9.4	42	.40	10.2	0.040	1.0	10.0	MW	CG	N
0.360	9.14	71130S	1.25	31.8	.280	7.1	12	2.1	.54	14	6.4	28	.40	10.2	0.040	1.0	10.0	SST	CG	N
0.360	9.14	71148	1.25	31.8	.276	7.0	17	3.0	.64	16	11	48	.43	10.8	0.042	1.1	10.1	MW	CG	N
0.360	9.14	71148S	1.25	31.8	.276	7.0	14	2.5	.51	13	7.3	33	.43	10.8	0.042	1.1	10.1	SST	CG	N
0.360	9.14	71166	1.25	31.8	.270	6.9	22	3.8	.60	15	13	59	.48	12.1	0.045	1.1	10.6	MW	CG	N
0.360	9.14	71166S	1.25	31.8	.270	6.9	19	3.3	.48	12	9.0	40	.48	12.1	0.045	1.1	10.6	SST	CG	N
0.360	9.14	71185	1.25	31.8	.266	6.8	28	4.9	.54	14	15	67	.48	12.2	0.047	1.2	10.3	MW	CG	N
0.360	9.14	71185S	1.25	31.8	.266	6.8	24	4.1	.43	11	10	45	.48	12.2	0.047	1.2	10.3	SST	CG	N
0.360	9.14	71207	1.25	31.8	.262	6.7	32	5.6	.53	13	17	76	.51	13.1	0.049	1.2	10.5	MW	CG	N
0.360	9.14	71207S	1.25	31.8	.262	6.7	27	4.8	.42	11	12	51	.51	13.1	0.049	1.2	10.5	SST	CG	N
0.360	9.14	71229	1.25	31.8	.258	6.6	37	6.5	.48	12	18	80	.55	14.1	0.051	1.3	10.9	MW	CG	N
0.360	9.14	71229S	1.25	31.8	.258	6.6	32	5.6	.38	9.7	12	54	.55	14.1	0.051	1.3	10.9	SST	CG	N
0.360	9.14	71251	1.25	31.8	.250	6.4	51	8.9	.44	11	22	99	.61	15.5	0.055	1.4	11.1	MW	CG	N
0.360	9.14	71251S	1.25	31.8	.250	6.4	43	7.5	.35	8.9	15	67	.61	15.5	0.055	1.4	11.1	SST	CG	N
0.360	9.14	71272	1.25	31.8	.242	6.1	68	12	.40	10	27	121	.67	17.0	0.059	1.5	11.4	MW	CG	N
0.360	9.14	71272S	1.25	31.8	.242	6.1	58	10	.32	8.2	18	82	.67	17.0	0.059	1.5	11.4	SST	CG	N
0.360	9.14	10450	1.28	32.5	.302	7.7	2.6	.45	.88	22	2.3	10	.41	10.3	0.029	0.7	13.0	MW	C	Z
0.360	9.14																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.360	9.14	71171	2.25	57.2	.270	6.9	12	2.1	1.1	29	13	59	.81	20.6	0.045	1.1	18.0	MW	CG	N
0.360	9.14	71171S	2.25	57.2	.270	6.9	10	1.7	.90	23	9.0	40	.81	20.6	0.045	1.1	18.0	SST	CG	N
0.360	9.14	71190	2.25	57.2	.266	6.8	15	2.6	1.0	26	15	67	.82	20.7	0.047	1.2	17.4	MW	CG	N
0.360	9.14	71190S	2.25	57.2	.266	6.8	13	2.2	.81	20	10	45	.82	20.7	0.047	1.2	17.4	SST	CG	N
0.360	9.14	10347	2.25	57.2	.264	6.7	22	3.9	.52	13	12	52	.65	16.5	0.048	1.2	13.5	SPR	CG	Z
0.360	9.14	71212	2.25	57.2	.262	6.7	17	3.0	.99	25	17	76	.88	22.4	0.049	1.2	18.0	MW	CG	N
0.360	9.14	71212S	2.25	57.2	.262	6.7	15	2.6	.79	20	12	51	.88	22.4	0.049	1.2	18.0	SST	CG	N
0.360	9.14	71234	2.25	57.2	.258	6.6	20	3.5	.90	23	18	80	.95	24.1	0.051	1.3	18.6	MW	CG	N
0.360	9.14	71234S	2.25	57.2	.258	6.6	17	3.0	.72	18	12	54	.95	24.1	0.051	1.3	18.6	SST	CG	N
0.360	9.14	71256	2.25	57.2	.250	6.4	27	4.7	.83	21	22	99	1.06	26.9	0.055	1.4	19.3	MW	CG	N
0.360	9.14	71256S	2.25	57.2	.250	6.4	23	4.0	.66	17	15	67	1.06	26.9	0.055	1.4	19.3	SST	CG	N
0.360	9.14	71277	2.25	57.2	.242	6.1	36	6.3	.76	19	27	121	1.17	29.6	0.059	1.5	19.8	MW	CG	N
0.360	9.14	71277S	2.25	57.2	.242	6.1	31	5.4	.60	15	18	82	1.17	29.6	0.059	1.5	19.8	SST	CG	N
0.360	9.14	U-61A	2.28	57.9	.272	6.9	10	1.8	.89	22	9.0	40	.88	22.4	0.044	1.1	19.0	SPR	C	Z
0.360	9.14	12229	2.34	59.5	.304	7.7	1.7	.30	1.9	48	3.3	15	.45	11.4	0.028	0.7	16.0	MW	CG	GI
0.360	9.14	S-1589	2.34	59.5	.284	7.2	3.7	.64	1.4	36	5.2	23	.91	23.2	0.038	1.0	24.0	SST	CG	N
0.360	9.14	71082	2.50	63.5	.296	7.5	3.3	.58	1.5	39	5.1	23	.48	12.1	0.032	0.8	14.9	MW	CG	N
0.360	9.14	71082S	2.50	63.5	.296	7.5	2.8	.49	1.2	31	3.4	15	.48	12.1	0.032	0.8	14.9	SST	CG	N
0.360	9.14	71100	2.50	63.5	.290	7.4	4.2	.74	1.5	38	6.3	28	.60	15.1	0.035	0.9	17.0	MW	CG	N
0.360	9.14	71100S	2.50	63.5	.290	7.4	3.6	.63	1.2	31	4.3	19	.60	15.1	0.035	0.9	17.0	SST	CG	N
0.360	9.14	71118	2.50	63.5	.284	7.2	5.8	1.0	1.4	36	8.1	36	.67	17.0	0.038	1.0	17.6	MW	CG	N
0.360	9.14	71118S	2.50	63.5	.284	7.2	4.9	.86	1.1	28	5.5	24	.67	17.0	0.038	1.0	17.6	SST	CG	N
0.360	9.14	71136	2.50	63.5	.280	7.1	6.7	1.2	1.4	36	9.4	42	.75	19.1	0.040	1.0	18.8	MW	CG	N
0.360	9.14	71136S	2.50	63.5	.280	7.1	5.7	1.0	1.1	28	6.4	28	.75	19.1	0.040	1.0	18.8	SST	CG	N
0.360	9.14	71154	2.50	63.5	.276	7.0	8.2	1.4	1.3	34	11	48	.80	20.3	0.042	1.1	19.0	MW	CG	N
0.360	9.14	71154S	2.50	63.5	.276	7.0	6.9	1.2	1.1	27	7.3	33	.80	20.3	0.042	1.1	19.0	SST	CG	N
0.360	9.14	3600	2.50	63.5	.270	6.9	10	1.8	1.3	34	13	59	.99	25.1	0.045	1.1	21.0	MW	C	Z
0.360	9.14	71172	2.50	63.5	.270	6.9	11	1.8	1.3	32	13	59	.89	22.7	0.045	1.1	19.9	MW	CG	N
0.360	9.14	71172S	2.50	63.5	.270	6.9	9.0	1.6	1.0	25	9.0	40	.89	22.7	0.045	1.1	19.9	SST	CG	N
0.360	9.14	71191	2.50	63.5	.266	6.8	13	2.3	1.1	29	15	67	.90	23.0	0.047	1.2	19.3	MW	CG	N
0.360	9.14	71191S	2.50	63.5	.266	6.8	11	2.0	.90	23	10	45	.90	23.0	0.047	1.2	19.3	SST	CG	N
0.360	9.14	3788	2.50	63.5	.264	6.7	10	1.8	1.1	29	12	52	1.30	32.9	0.048	1.2	27.0	SPR	CG	Z
0.360	9.14	71213	2.50	63.5	.262	6.7	15	2.7	1.1	28	17	76	.97	24.7	0.049	1.2	19.9	MW	CG	N
0.360	9.14	71213S	2.50	63.5	.262	6.7	13	2.3	.88	22	12	51	.97	24.7	0.049	1.2	19.9	SST	CG	N
0.360	9.14	12473	2.50	63.5	.260	6.6	15	2.7	.80	20	12	54	1.10	27.9	0.050	1.3	22.0	SPR	CG	Z
0.360	9.14	71235	2.50	63.5	.258	6.6	18	3.1	1.0	25	18	80	1.04	26.4	0.051	1.3	20.4	MW	CG	N
0.360	9.14	71235S	2.50	63.5	.258	6.6	15	2.7	.80	20	12	54	1.04	26.4	0.051	1.3	20.4	SST	CG	N
0.360	9.14	71257	2.50	63.5	.250	6.4	24	4.2	.92	23	22	99	1.17	29.7	0.055	1.4	21.3	MW	CG	N
0.360	9.14	71257S	2.50	63.5	.250	6.4	20	3.6	.74	19	15	67	1.17	29.7	0.055	1.4	21.3	SST	CG	N
0.360	9.14	71278	2.50	63.5	.242	6.1	32	5.6	.85	22	27	121	1.29	32.8	0.059	1.5	21.9	MW	CG	N
0.360	9.14	71278S	2.50	63.5	.242	6.1	27	4.8	.68	17	18	82	1.29	32.8	0.059	1.5	21.9	SST	CG	N
0.360	9.14	LL-12	2.63	66.7	.180	4.6	262	46	.22	5.7	59	260	1.85	46.9	0.090	2.3	20.5	SPR	CG	Z
0.360	9.14	B10-53	2.69	68.2	.274	7.0	9.7	1.7	.86	22	8.4	37	.82	20.8	0.043	1.1	18.0	SPR	C	BO
0.360	9.14	3940	2.69	68.2	.252	6.4	21	3.7	.72	18	15	68	1.20	30.5	0.054	1.4	22.3	SPR	CG	Z
0.360	9.14	71173	2.75	69.9	.270	6.9	9.6	1.7	1.4	35	13	59	.97	24.7	0.045	1.1	21.6	MW	CG	N
0.360	9.14	71173S	2.75	69.9	.270	6.9	8.2	1.4	1.1	28	9.0	40	.97	24.7	0.045	1.1	21.6	SST	CG	N
0.360	9.14	71192	2.75	69.9	.266	6.8	12	2.1	1.2	32	15	67	.98	24.9	0.047	1.2	20.9	MW	CG	N
0.360	9.14	71192S	2.75	69.9	.266	6.8	10	1.8	.99	25	10	45	.98	24.9	0.047	1.2	20.9	SST	CG	N
0.360	9.14	71214	2.75	69.9	.262	6.7	14	2.5	1.2	31	17	76	1.06	26.9	0.049	1.2	21.6	MW	CG	N
0.360	9.14	71214S	2.75	69.9	.262	6.7	12	2.1	.97	25	12	51	1.06	26.9	0.049	1.2	21.6	SST	CG	N
0.360	9.14	71236	2.75	69.9	.258	6.6	16	2.8	1.1	28	18	80	1.14	29.0	0.051	1.3	22.4	MW	CG	N
0.360	9.14	71236S	2.75	69.9	.258	6.6	14	2.4	.88	22	12	54	1.14	29.0	0.051	1.3	22.4	SST	CG	N
0.360	9.14	71258	2.75	69.9	.250	6.4	22	3.8	1.0	26	22	99	1.28	32.5	0.055	1.4	23.3	MW	CG	N
0.360	9.14	71258S	2.75	69.9	.250	6.4	19	3.3	.81	21	15	67	1.28	32.5	0.055	1.4	23.3	SST	CG	N
0.360	9.14	71279	2.75	69.9	.242	6.1	29	5.1	.94	24	27	121	1.42	36.0	0.059	1.5	24.0	MW	CG	N
0.360	9.14	71279S	2.75	69.9	.242	6.1	25	4.3	.75	19	18	82	1.42	36.0	0.059	1.5	24.0	SST	CG	N
0.360	9.14	4318	2.81	71.4	.272	6.9	7.4	1.3	1.2	31	9.0	40	1.16	29.3	0.044	1.1	25.3	SPR	C	Z
0.360	9.14	10642	2.88	73.0	.270	6.9	7.6	1.3	1.3	32	9.6	43	1.26	32.0	0.045	1.1	27.0	SPR	C	Z
0.360	9.14	LL-32	2.88	73.0	.240	6.1	25	4.3	.78	20	19	86	1.62	41.1	0.060	1.5	27.0	SST	CG	N
0.360	9.14	12154	3.00	76.2	.274	7.0	5.8	1.0	1.5	37	8.4	37	1.25	31.7	0.043	1.1	29.0	SPR	CG	Z
0.360	9.14	71193	3.00	76.2	.266	6.8	11	1.9	1.4	35	15	67	1.07	27.2	0.047	1.2	22.8	MW	CG	N
0.360	9.14	71193S	3.00	76.2	.266	6.8	9.4	1.6	1.1	28	10	45	1.07	27.2	0.047	1.2	22.8	SST	CG	N
0.360	9.14	71215	3.00	76.2	.262	6.7	13	2.2	1.3	34	17	76	1.15	29.2	0.049	1.2	23.5	MW	CG	N
0.360	9.14	71215S	3.00	76.2	.262	6.7	11	1.9	1.1	27	12	51	1.15	29.2	0.049	1.2	23.5	SST	CG	N
0.360	9.14	71237	3.00	76.2	.258	6.6	15	2.6	1.2	31	18	80	1.24	31.4	0.051	1.3	24.3	MW	CG	N
0.360	9.14	71237S	3.00	76.2	.258	6.6	13	2.2	.96	24	12	54	1.24	31.4	0.051	1.3	24.3	SST	CG	N
0.360	9.14	71259	3.00	76.2	.250	6.4	20	3.5	1.1	28	22	99	1.39	35.3	0.055	1.4	25.3	MW	CG	N
0.360	9.14																			




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.360	9.14	71281S	3.25	82.6	.242	6.1	21	3.6	.89	23	18	82	1.66	42.1	0.059	1.5	28.1	SST	CG	N
0.360	9.14	10850	3.50	88.9	.280	7.1	5.0	.88	1.3	32	6.4	28	.88	22.4	0.040	1.0	22.0	SST	CG	N
0.360	9.14	71195	3.50	88.9	.266	6.8	9.4	1.6	1.6	41	15	67	1.24	31.5	0.047	1.2	26.4	MW	CG	N
0.360	9.14	71195S	3.50	88.9	.266	6.8	8.6	1.4	1.3	32	10	45	1.24	31.5	0.047	1.2	26.4	SST	CG	N
0.360	9.14	71217	3.50	88.9	.262	6.7	11	1.9	1.6	40	17	76	1.34	33.9	0.049	1.2	27.3	MW	CG	N
0.360	9.14	71217S	3.50	88.9	.262	6.7	9.3	1.6	1.2	32	12	51	1.34	33.9	0.049	1.2	27.3	SST	CG	N
0.360	9.14	71239	3.50	88.9	.258	6.6	13	2.2	1.4	36	18	80	1.43	36.4	0.051	1.3	28.1	MW	CG	N
0.360	9.14	71239S	3.50	88.9	.258	6.6	11	1.9	1.1	29	12	54	1.43	36.4	0.051	1.3	28.1	SST	CG	N
0.360	9.14	71261	3.50	88.9	.250	6.4	17	3.0	1.3	33	22	99	1.60	40.7	0.055	1.4	29.1	MW	CG	N
0.360	9.14	71261S	3.50	88.9	.250	6.4	15	2.5	1.0	26	15	67	1.60	40.7	0.055	1.4	29.1	SST	CG	N
0.360	9.14	71282	3.50	88.9	.242	6.1	23	4.0	1.2	31	27	121	1.78	45.1	0.059	1.5	30.1	MW	CG	N
0.360	9.14	71282S	3.50	88.9	.242	6.1	19	3.4	.96	24	18	82	1.78	45.1	0.059	1.5	30.1	SST	CG	N
0.360	9.14	UU-54	3.75	95.3	.290	7.4	2.0	.35	2.3	59	4.6	20	1.23	31.1	0.035	0.9	34.0	SPR	C	Z
0.360	9.14	2907	4.00	101.6	.180	4.6	148	26	.40	10	59	260	3.13	79.4	0.090	2.3	34.8	SPR	CG	Z
0.360	9.14	L-33	4.13	104.8	.266	6.8	6.1	1.1	1.8	46	11	48	1.88	47.8	0.047	1.2	40.0	SPR	CG	Z
0.360	9.14	11422	4.38	111.1	.300	7.6	.91	.16	3.2	81	2.9	13	1.17	29.7	0.030	0.8	38.0	MW	C	Z
0.360	9.14	11515	4.81	122.2	.292	7.4	1.7	.31	2.5	64	4.4	20	1.19	30.2	0.034	0.9	34.0	SPR	C	Z
0.360	9.14	3053	4.88	123.8	.266	6.8	5.4	.94	2.0	51	11	48	2.12	53.7	0.047	1.2	45.0	HD	CG	Z
0.360	9.14	12265	5.25	133.4	.236	6.0	32	5.7	.70	18	23	101	1.67	42.5	0.062	1.6	27.0	SPR	CG	GI
0.360	9.14	12117	6.25	158.8	.282	7.2	2.1	.37	3.0	76	6.3	28	1.99	50.5	0.039	1.0	50.0	SPR	C	Z
0.360	9.14	2623	6.50	165.1	.284	7.2	2.0	.36	2.9	73	5.8	26	1.81	45.8	0.038	1.0	46.5	SPR	C	Z
0.360	9.14	12202	7.63	193.7	.264	6.7	3.8	.66	3.1	78	12	52	3.36	85.3	0.048	1.2	69.0	SPR	C	Z
0.362	9.19	12745	1.19	30.1	.290	7.4	7.7	1.4	.76	19	5.8	26	.43	11.0	0.036	0.9	11.0	MW	C	N
0.364	9.25	12694	2.25	57.2	.264	6.7	18	3.2	.92	23	17	74	.95	24.1	0.050	1.3	18.0	MW	C	BO
0.370	9.40	B4-61	.88	22.2	.314	8.0	5.5	.96	.41	10	2.3	10	.18	4.6	0.028	0.7	5.50	SST	C	N
0.375	9.53	BB-89*	.19	4.8	.335	8.5	8.9	1.6	.10	2.4	.86	3.8	.07	1.8	0.020	0.5	2.50	SPR	C	N
0.375	9.53	4104	.25	6.4	.291	7.4	121	21	.06	1.6	7.5	34	.13	3.2	0.042	1.1	3.00	SPR	CG	Z
0.375	9.53	3289	.28	7.1	.299	7.6	39	6.9	.09	2.3	3.6	16	.19	4.8	0.038	1.0	4.00	SPR	C	Z
0.375	9.53	10183	.31	7.9	.347	8.8	.78	.14	.25	6.3	.19	87	.06	1.6	0.014	0.4	3.50	MW	C	Z
0.375	9.53	S-1315	.38	9.5	.315	8.0	25	4.3	.11	2.8	2.7	12	.12	3.0	0.030	0.8	3.00	SST	C	N
0.375	9.53	K-20	.38	9.5	.305	7.7	27	4.8	.16	4.1	4.4	20	.18	4.4	0.035	0.9	4.00	SPR	C	GI
0.375	9.53	K-69	.38	9.5	.293	7.4	32	5.5	.17	4.3	5.4	24	.21	5.2	0.041	1.0	5.00	SST	CG	N
0.375	9.53	A-32	.38	9.5	.285	7.2	66	11	.14	3.6	9.2	41	.20	5.1	0.045	1.1	4.50	SPR	CG	N
0.375	9.53	A10-38	.38	9.5	.273	6.9	127	22	.09	2.3	12	52	.20	5.2	0.051	1.3	4.00	SST	CG	N
0.375	9.53	S-166	.38	9.5	.265	6.7	116	20	.10	2.5	12	52	.28	7.0	0.055	1.4	5.00	SST	CG	N
0.375	9.53	10634	.41	10.3	.315	8.0	20	3.5	.14	3.4	2.7	12	.13	3.3	0.030	0.8	3.25	SST	C	N
0.375	9.53	B2-47	.42	10.7	.279	7.1	87	15	.13	3.2	11	50	.26	6.7	0.048	1.2	4.50	SPR	C	N
0.375	9.53	H-4	.44	11.1	.291	7.4	42	7.4	.17	4.3	7.1	31	.19	4.8	0.042	1.1	4.50	SST	CG	N
0.375	9.53	10132	.44	11.1	.285	7.2	66	11	.14	3.6	9.2	41	.20	5.2	0.045	1.1	4.50	SPR	CG	Z
0.375	9.53	V-38	.44	11.1	.285	7.2	82	14	.11	2.9	9.2	41	.18	4.6	0.045	1.1	4.00	SPR	CG	Z
0.375	9.53	B4-17	.44	11.1	.279	7.1	87	15	.13	3.2	11	50	.26	6.7	0.048	1.2	4.50	SPR	C	N
0.375	9.53	3666	.47	11.9	.327	8.3	3.3	.58	.34	8.6	1.1	5.0	.13	3.2	0.024	0.6	5.33	MW	C	Z
0.375	9.53	AA-66	.47	11.9	.305	7.7	16	2.8	.25	6.5	4.1	18	.21	5.3	0.035	0.9	5.00	SST	C	N
0.375	9.53	O-61	.47	11.9	.295	7.5	33	5.7	.20	5.1	6.5	29	.24	6.1	0.040	1.0	5.00	SPR	C	N
0.375	9.53	F-33	.47	11.9	.285	7.2	94	16	.10	2.5	9.2	41	.21	5.4	0.045	1.1	4.75	SPR	C	Z
0.375	9.53	TT-36	.47	11.9	.283	7.2	52	9.0	.19	4.8	9.8	44	.25	6.4	0.046	1.2	5.50	SPR	CG	Z
0.375	9.53	A-20	.47	11.9	.275	7.0	58	10	.17	4.3	9.7	43	.30	7.6	0.050	1.3	6.00	SST	CG	N
0.375	9.53	2583	.50	12.7	.335	8.5	2.1	.36	.39	9.9	.80	3.6	.11	2.8	0.020	0.5	4.50	MW	C	Z
0.375	9.53	N-36	.50	12.7	.335	8.5	1.8	.31	.39	9.9	.70	3.1	.11	2.8	0.020	0.5	4.50	SST	C	N
0.375	9.53	PP-71	.50	12.7	.335	8.5	.82	.14	.32	8.0	.26	1.2	.19	4.7	0.020	0.5	8.25	MW	C	BO
0.375	9.53	NN-38	.50	12.7	.333	8.5	.90	.16	.29	7.4	.26	1.2	.21	5.3	0.021	0.5	9.00	MW	C	N
0.375	9.53	B12-33	.50	12.7	.331	8.4	1.9	.34	.37	9.3	.70	3.1	.13	3.4	0.022	0.6	6.00	MW	CG	N
0.375	9.53	4254	.50	12.7	.329	8.4	1.7	.29	.30	7.7	.51	2.3	.20	5.0	0.023	0.6	7.50	MW	C	Z
0.375	9.53	K-5	.50	12.7	.323	8.2	2.6	.45	.27	6.8	.69	3.0	.23	5.9	0.026	0.7	8.00	MW	C	Z
0.375	9.53	CC-46	.50	12.7	.311	7.9	8.1	1.4	.28	7.0	2.2	10	.22	5.7	0.032	0.8	6.00	SST	C	N
0.375	9.53	S-1184	.50	12.7	.303	7.7	20	3.4	.23	5.8	4.5	20	.17	4.3	0.036	0.9	4.75	SST	CG	N
0.375	9.53	BB-6	.50	12.7	.301	7.6	17	3.0	.26	6.6	4.5	20	.24	6.1	0.037	0.9	5.50	SST	C	N
0.375	9.53	10153	.50	12.7	.293	7.4	31	5.5	.23	5.7	7.0	31	.23	5.7	0.041	1.0	5.50	SPR	CG	Z
0.375	9.53	S-837	.50	12.7	.293	7.4	32	5.5	.21	5.3	6.6	29	.21	5.2	0.041	1.0	5.00	SST	CG	N
0.375	9.53	EE-50	.50	12.7	.293	7.4	44	7.6	.16	4.1	7.0	31	.23	5.7	0.041	1.0	4.50	SPR	C	N
0.375	9.53	938	.50	12.7	.281	7.1	99	17	.11	2.7	10	47	.24	6.0	0.047	1.2	4.00	HD	C	Z
0.375	9.53	K-96	.50	12.7	.281	7.1	57	9.9	.18	4.7	10	47	.26	6.6	0.047	1.2	5.50	SPR	CG	N
0.375	9.53	MM-77	.50	12.7	.275	7.0	65	11	.17	4.3	11	49	.28	7.0	0.050	1.3	5.50	SST	CG	N
0.375	9.53	FF-18	.50	12.7	.275	7.0	105	18	.11	2.8	12	52	.23	5.7	0.050	1.3	4.50	SPR	CG	N
0.375	9.53	PP-4	.50	12.7	.265	6.7	100	18	.15	3.9	15	69	.33	8.4	0.055	1.4	6.00	SPR	CG	Z
0.375	9.53	S-312	.50	12.7	.265	6.7	112	20	.13	3.3	15	65	.28	7.2	0.055	1.4	5.00	SST	CG	N
0.375	9.53	939	.50	12.7	.251	6.4	231	40	.09	2.4	22	97	.31	7.9	0.062	1.6	5.00	HD	CG	Z
0.375	9.53	S-1477	.50	12.7	.251	6.4	201	35	.10	2.6	21	92	.31	7.9	0.062	1.6	5.00	SST	CG	N
0.375	9.53	S-1119	.50	12.7																



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.375	9.53	10581	.56	14.3	.317	8.1	7.6	1.3	.41	10	3.1	14	.15	3.9	0.029	0.7	5.25	MW	CG	Z
0.375	9.53	2654	.56	14.3	.299	7.6	26	4.6	.22	5.5	5.6	25	.19	4.8	0.038	1.0	5.00	SPR	CG	Z
0.375	9.53	1891	.56	14.3	.285	7.2	41	7.2	.23	5.7	9.2	41	.27	6.9	0.045	1.1	6.00	SPR	CG	Z
0.375	9.53	0-75	.56	14.3	.283	7.2	45	7.9	.22	5.5	9.8	44	.28	7.0	0.046	1.2	6.00	SPR	CG	N
0.375	9.53	J-56	.56	14.3	.281	7.1	50	8.8	.19	5.0	9.8	44	.31	7.8	0.047	1.2	5.50	SST	C	N
0.375	9.53	I-33	.56	14.3	.277	7.0	80	14	.15	3.8	12	53	.29	7.5	0.049	1.2	5.00	SPR	C	N
0.375	9.53	B15-17	.56	14.3	.211	5.4	646	113	.07	1.8	45	201	.49	12.5	0.082	2.1	6.00	SPR	CG	N
0.375	9.53	W-15	.59	15.1	.323	8.2	2.4	.42	.35	8.8	.82	3.7	.25	6.3	0.026	0.7	8.50	MW	C	N
0.375	9.53	S-908	.59	15.1	.301	7.6	15	2.7	.31	8.0	4.9	22	.22	5.6	0.037	0.9	6.00	SST	CG	N
0.375	9.53	B14-7	.59	15.1	.289	7.3	38	6.7	.21	5.4	8.1	36	.24	6.0	0.043	1.1	5.50	SPR	CG	N
0.375	9.53	B12-48	.63	15.9	.347	8.8	.59	.10	.56	14	.33	1.4	.07	1.8	0.014	0.4	4.00	MW	C	N
0.375	9.53	00-63	.63	15.9	.335	8.5	1.5	.26	.51	13	.75	3.3	.12	3.0	0.020	0.5	5.00	SST	C	N
0.375	9.53	HH-80	.63	15.9	.331	8.4	1.7	.30	.46	12	.78	3.5	.17	4.2	0.022	0.6	6.50	MW	C	N
0.375	9.53	0-90	.63	15.9	.327	8.3	1.6	.28	.41	10	.65	2.9	.22	5.5	0.024	0.6	8.00	SST	C	N
0.375	9.53	12433	.63	15.9	.323	8.2	5.2	.90	.47	12	2.4	11	.16	4.0	0.026	0.7	5.00	MW	C	GI
0.375	9.53	G-95	.63	15.9	.323	8.2	2.4	.42	.40	10	.96	4.3	.22	5.6	0.026	0.7	8.50	MW	CG	N
0.375	9.53	10305	.63	15.9	.317	8.1	3.5	.61	.34	8.5	1.2	5.2	.29	7.4	0.029	0.7	9.00	MW	C	Z
0.375	9.53	Z-8	.63	15.9	.315	8.0	4.7	.83	.39	9.8	1.8	8.1	.24	6.1	0.030	0.8	8.00	MW	CG	Z
0.375	9.53	2603	.63	15.9	.303	7.7	15	2.7	.37	9.5	5.8	26	.25	6.4	0.036	0.9	6.00	MW	C	Z
0.375	9.53	KK-38	.63	15.9	.295	7.5	17	2.9	.34	8.5	5.5	25	.29	7.4	0.040	1.0	7.25	SST	CG	N
0.375	9.53	BB-54	.63	15.9	.289	7.3	34	5.9	.24	6.1	8.1	36	.26	6.6	0.043	1.1	6.00	SPR	CG	Z
0.375	9.53	516	.63	15.9	.281	7.1	46	8.0	.23	5.8	10	47	.34	8.8	0.047	1.2	6.33	HD	C	Z
0.375	9.53	H-60-A	.63	15.9	.281	7.1	36	6.3	.27	6.9	9.8	44	.35	9.0	0.047	1.2	7.50	SPR	CG	Z
0.375	9.53	S-3027	.63	15.9	.273	6.9	68	12	.17	4.4	12	52	.34	8.7	0.051	1.3	5.75	SST	C	N
0.375	9.53	G-97	.63	15.9	.263	6.7	145	25	.11	2.9	16	73	.34	8.5	0.056	1.4	5.00	SPR	C	N
0.375	9.53	RR-12	.63	15.9	.255	6.5	119	21	.15	3.7	17	77	.48	12.2	0.060	1.5	7.00	MW	C	N
0.375	9.53	507	.63	15.9	.251	6.4	160	28	.14	3.5	22	97	.45	11.5	0.062	1.6	6.33	HD	C	Z
0.375	9.53	F-46	.63	15.9	.249	6.3	186	33	.12	3.1	23	102	.38	9.6	0.063	1.6	6.00	HD	CG	Z
0.375	9.53	K-70	.63	15.9	.231	5.9	278	49	.11	2.9	32	142	.50	12.8	0.072	1.8	7.00	SPR	CG	Z
0.375	9.53	11311	.63	15.9	.225	5.7	421	74	.08	2.2	36	159	.45	11.4	0.075	1.9	6.00	SPR	CG	N
0.375	9.53	S-1689	.64	16.3	.325	8.3	5.7	1.0	.28	7.1	1.6	7.1	.13	3.2	0.025	0.6	4.00	SST	C	N
0.375	9.53	1785	.66	16.7	.323	8.2	5.2	.90	.50	13	2.6	11	.16	4.0	0.026	0.7	5.00	MW	C	Z
0.375	9.53	12655	.66	16.7	.323	8.2	5.6	.98	.47	12	2.7	12	.15	3.8	0.026	0.7	4.75	MW	C	N
0.375	9.53	2769	.66	16.7	.211	5.4	704	123	.09	2.3	64	285	.55	13.9	0.082	2.1	5.67	MW	C	Z
0.375	9.53	12429	.69	17.4	.327	8.3	3.7	.64	.54	14	2.0	8.9	.14	3.7	0.024	0.6	5.00	MW	C	GI
0.375	9.53	12421	.69	17.4	.321	8.2	6.0	1.1	.49	13	3.0	13	.16	4.1	0.027	0.7	5.00	MW	C	N
0.375	9.53	S-892	.69	17.4	.311	7.9	4.1	.71	.34	8.5	1.4	6.0	.35	8.9	0.032	0.8	10.0	SST	C	N
0.375	9.53	3637	.69	17.4	.305	7.7	11	1.9	.40	10	4.4	20	.28	7.1	0.035	0.9	7.00	SPR	C	Z
0.375	9.53	B12-26	.69	17.4	.305	7.7	14	2.4	.32	8.2	4.4	20	.21	5.3	0.035	0.9	6.00	SPR	CG	N
0.375	9.53	A15-3	.69	17.4	.297	7.5	21	3.6	.29	7.5	6.1	27	.24	6.2	0.039	1.0	6.25	SPR	CG	N
0.375	9.53	I-85	.69	17.4	.283	7.2	28	4.9	.25	6.4	7.0	31	.44	11.1	0.046	1.2	8.50	SPR	C	N
0.375	9.53	KK-8	.69	17.4	.271	6.9	62	11	.21	5.4	13	58	.36	9.2	0.052	1.3	7.00	SPR	CG	Z
0.375	9.53	H-11	.69	17.4	.251	6.4	173	30	.13	3.2	22	97	.37	9.4	0.062	1.6	6.00	SPR	CG	Z
0.375	9.53	A12-15	.70	17.9	.333	8.5	.55	.10	.40	10	.22	.97	.31	7.7	0.021	0.5	13.5	MW	C	N
0.375	9.53	4252	.75	19.1	.343	8.7	.34	.06	.61	15	.21	.91	.14	3.7	0.016	0.4	8.00	MW	C	Z
0.375	9.53	FF-52	.75	19.1	.341	8.7	.24	.04	.54	14	.13	.57	.21	5.4	0.017	0.4	11.5	SST	C	N
0.375	9.53	S-7	.75	19.1	.335	8.5	.75	.13	.57	14	.42	1.9	.18	4.6	0.020	0.5	8.00	SST	C	N
0.375	9.53	B2-7	.75	19.1	.333	8.5	.55	.10	.45	11	.24	1.1	.31	7.7	0.021	0.5	13.5	MW	CL	N
0.375	9.53	GG-99	.75	19.1	.325	8.3	2.8	.50	.56	14	1.6	7.1	.18	4.4	0.025	0.6	6.00	SST	C	N
0.375	9.53	G-99	.75	19.1	.323	8.2	5.2	.90	.52	13	2.7	12	.16	4.0	0.026	0.7	5.00	MW	C	N
0.375	9.53	A-51	.75	19.1	.319	8.1	3.7	.64	.55	14	2.0	9.1	.20	5.0	0.028	0.7	7.00	SST	CG	N
0.375	9.53	526	.75	19.1	.313	8.0	7.7	1.3	.42	11	3.2	14	.22	5.7	0.031	0.8	6.25	HD	C	Z
0.375	9.53	A-70	.75	19.1	.297	7.5	17	3.0	.34	8.5	5.7	25	.25	6.4	0.039	1.0	6.50	SST	CG	N
0.375	9.53	I-12	.75	19.1	.295	7.5	24	4.3	.27	6.8	6.5	29	.24	6.1	0.040	1.0	6.00	SPR	CG	GI
0.375	9.53	B2-70	.75	19.1	.295	7.5	24	4.3	.37	9.4	9.0	40	.28	7.1	0.040	1.0	6.00	MW	C	N
0.375	9.53	291	.75	19.1	.293	7.4	23	4.0	.31	7.8	7.0	31	.32	8.1	0.041	1.0	6.75	HD	C	Z
0.375	9.53	S-740	.75	19.1	.291	7.4	22	3.9	.32	8.1	7.1	31	.33	8.3	0.042	1.1	6.75	SST	C	N
0.375	9.53	12234	.75	19.1	.291	7.4	24	4.2	.31	7.9	7.5	34	.34	8.5	0.042	1.1	7.00	SPR	C	Z
0.375	9.53	B15-61	.75	19.1	.285	7.2	30	5.2	.31	7.9	9.2	41	.38	9.7	0.045	1.1	7.50	SPR	C	N
0.375	9.53	F-37	.75	19.1	.283	7.2	36	6.3	.27	6.9	9.8	44	.37	9.3	0.046	1.2	7.00	HD	C	Z
0.375	9.53	II-79	.75	19.1	.281	7.1	31	5.4	.30	7.7	9.3	41	.45	11.3	0.047	1.2	8.50	SPR	C	Z
0.375	9.53	2557	.75	19.1	.279	7.1	35	6.1	.35	9.0	12	55	.40	10.1	0.048	1.2	8.25	MW	CG	Z
0.375	9.53	4358	.75	19.1	.275	7.0	65	11	.18	4.6	12	52	.35	8.9	0.050	1.3	6.00	SPR	C	Z
0.375	9.53	367	.75	19.1	.267	6.8	67	12	.22	5.5	15	65	.46	11.7	0.054	1.4	7.50	HD	C	Z
0.375	9.53	KK-39	.75	19.1	.247	6.3	146	26	.16	4.2	24	107	.48	12.2	0.064	1.6	7.50	SPR	CG	Z
0.375	9.53	10905	.78	19.8	.343	8.7	.33	.06	.63	16	.21	.92	.15	3.8	0.016	0.4	8.25	MW	C	N
0.375	9.53	S-342	.78	19.8	.325	8.3	1.7	.29	.56	14	.92	4.1	.23	5.7	0.025	0.6	9.00	SST	CG	N
0.375	9.53	A10-11	.78	19.8	.285	7.2	24	4.2	.36	9.1	8.6	38	.41	10.3	0.045	1.1	8.00	SST	C	N
0.375	9.53	L-45	.78	19.8	.267	6.8	67	12	.22	5.5	15	65	.41	10.3	0.054	1.4	7.50	SPR	CG	N
0.375	9.53	940	.81	20.6	.329	8.4	2.6	.46	.66	17	1.7	7.8								




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.375	9.53	3093	.88	22.2	.319	8.1	3.6	.63	.63	16	2.3	10	.25	6.3	0.028	0.7	7.75	MW	C	Z
0.375	9.53	S-46	.88	22.2	.317	8.1	1.4	.25	.35	9.0	.50	2.2	.52	13.3	0.029	0.7	17.0	SST	C	N
0.375	9.53	I-89	.88	22.2	.315	8.0	4.1	.71	.61	15	2.5	11	.27	6.9	0.030	0.8	9.00	MW	CG	Z
0.375	9.53	DD-90	.88	22.2	.315	8.0	3.9	.68	.59	15	2.3	10	.29	7.2	0.030	0.8	8.50	SST	C	N
0.375	9.53	2571	.88	22.2	.313	8.0	3.3	.57	.47	12	1.5	6.8	.40	10.2	0.031	0.8	12.0	MW	C	Z
0.375	9.53	S-736	.88	22.2	.311	7.9	7.2	1.3	.46	12	3.3	15	.24	6.1	0.032	0.8	6.50	SST	C	N
0.375	9.53	N-95	.88	22.2	.305	7.7	4.8	.84	.46	12	2.2	9.7	.42	10.7	0.035	0.9	12.0	SST	CG	N
0.375	9.53	UU-33	.88	22.2	.297	7.5	16	2.8	.38	9.7	6.1	27	.33	8.4	0.039	1.0	7.50	SPR	C	Z
0.375	9.53	S-741	.88	22.2	.291	7.4	19	3.4	.37	9.4	7.1	31	.36	9.1	0.042	1.1	7.50	SST	C	N
0.375	9.53	3616	.88	22.2	.281	7.1	33	5.8	.32	8.0	10	47	.42	10.7	0.047	1.2	8.00	HD	C	Z
0.375	9.53	B14-59	.88	22.2	.271	6.9	69	12	.19	4.8	13	58	.39	9.9	0.052	1.3	6.50	SPR	C	Z
0.375	9.53	Y-25	.88	22.2	.255	6.5	86	15	.22	5.5	19	83	.48	12.2	0.060	1.5	8.00	SST	CG	N
0.375	9.53	885	.88	22.2	.215	5.5	328	57	.13	3.3	43	190	.72	18.3	0.080	2.0	9.00	HD	CG	Z
0.375	9.53	B9-15	.91	23.0	.317	8.1	4.6	.81	.69	18	3.2	14	.21	5.4	0.029	0.7	7.33	MW	CG	GI
0.375	9.53	S-492	.91	23.0	.305	7.7	6.0	1.0	.56	14	3.3	15	.35	8.9	0.035	0.9	10.0	SST	CG	N
0.375	9.53	B3-38	.91	23.0	.269	6.8	52	9.2	.27	6.8	14	62	.45	11.4	0.053	1.3	8.50	SPR	CG	N
0.375	9.53	K-42	.94	23.8	.335	8.5	1.1	.20	.77	20	.86	3.8	.14	3.6	0.020	0.5	6.00	SST	C	N
0.375	9.53	10263	.94	23.8	.325	8.3	4.8	.83	.50	13	2.4	11	.14	3.7	0.025	0.6	4.75	MW	CG	Z
0.375	9.53	A11-58	.94	23.8	.315	8.0	5.4	.95	.73	18	4.0	18	.21	5.3	0.030	0.8	7.00	MW	CG	N
0.375	9.53	F-38	.94	23.8	.285	7.2	23	4.1	.39	10	9.2	41	.45	11.4	0.045	1.1	9.00	SPR	C	Z
0.375	9.53	O-45	.94	23.8	.281	7.1	33	5.8	.32	8.0	10	47	.42	10.7	0.047	1.2	8.00	SPR	C	Z
0.375	9.53	12310	.94	23.8	.279	7.1	36	6.4	.31	7.8	11	50	.43	11.0	0.048	1.2	8.00	SPR	C	Z
0.375	9.53	S-1008	.94	23.8	.273	6.9	38	6.6	.31	7.9	12	52	.45	11.3	0.051	1.3	8.75	SST	CG	N
0.375	9.53	2928	.94	23.8	.251	6.4	77	13	.26	6.5	20	88	.68	17.3	0.062	1.6	11.0	HD	CG	GI
0.375	9.53	B11-36	.97	24.6	.319	8.1	2.1	.37	.63	16	1.3	5.9	.34	8.5	0.028	0.7	12.0	MW	CG	N
0.375	9.53	A-78	1.00	25.4	.335	8.5	.48	.08	.76	19	.36	1.6	.25	6.2	0.020	0.5	11.3	SST	C	N
0.375	9.53	H-7	1.00	25.4	.327	8.3	1.2	.21	.74	19	.88	3.9	.26	6.7	0.024	0.6	10.0	SST	C	N
0.375	9.53	3230	1.00	25.4	.315	8.0	4.4	.76	.72	18	3.1	14	.29	7.2	0.030	0.8	8.50	MW	C	Z
0.375	9.53	HH-74	1.00	25.4	.315	8.0	5.0	.88	.54	14	2.7	12	.24	6.1	0.030	0.8	7.00	SST	C	N
0.375	9.53	U-26	1.00	25.4	.315	8.0	3.0	.52	.63	16	1.9	8.3	.38	9.5	0.030	0.8	11.5	MW	C	N
0.375	9.53	S-737	1.00	25.4	.311	7.9	6.2	1.1	.53	14	3.3	15	.26	6.7	0.032	0.8	7.25	SST	C	N
0.375	9.53	10763	1.00	25.4	.305	7.7	5.4	.95	.58	15	3.1	14	.42	10.7	0.035	0.9	11.0	SST	C	N
0.375	9.53	O-156	1.00	25.4	.297	7.5	11	1.9	.55	14	6.1	27	.43	10.9	0.039	1.0	10.0	SPR	C	GI
0.375	9.53	3577	1.00	25.4	.293	7.4	14	2.4	.55	14	7.5	33	.45	11.5	0.041	1.0	10.0	MW	C	GI
0.375	9.53	3595	1.00	25.4	.291	7.4	17	3.0	.57	15	9.8	43	.43	10.8	0.042	1.1	9.00	MW	C	GI
0.375	9.53	S-742	1.00	25.4	.291	7.4	16	2.8	.44	11	7.1	31	.40	10.1	0.042	1.1	8.50	SST	C	N
0.375	9.53	XX-64	1.00	25.4	.289	7.3	17	2.9	.48	12	8.1	36	.47	12.0	0.043	1.1	10.0	SPR	C	Z
0.375	9.53	TT-58	1.00	25.4	.285	7.2	18	3.2	.46	12	8.4	37	.54	13.7	0.045	1.1	11.0	SPR	C	GI
0.375	9.53	B15-39	1.00	25.4	.285	7.2	18	3.2	.48	12	8.6	38	.50	12.6	0.045	1.1	10.0	SST	C	N
0.375	9.53	200	1.00	25.4	.281	7.1	27	4.6	.40	10	10	47	.49	12.5	0.047	1.2	9.50	HD	C	Z
0.375	9.53	Z-37	1.00	25.4	.281	7.1	22	3.8	.45	12	9.8	44	.47	11.9	0.047	1.2	10.0	SST	CG	N
0.375	9.53	L-10	1.00	25.4	.249	6.3	166	29	.14	3.5	23	102	.41	10.4	0.063	1.6	6.50	SPR	CG	N
0.375	9.53	10220	1.00	25.4	.231	5.9	174	30	.18	4.7	32	142	.72	18.3	0.072	1.8	10.0	SPR	CG	GI
0.375	9.53	B3-42	1.00	25.4	.215	5.5	353	62	.12	3.1	43	190	.76	19.3	0.080	2.0	8.50	SPR	C	N
0.375	9.53	4290	1.03	26.2	.313	8.0	4.7	.82	.75	19	3.5	16	.28	7.1	0.031	0.8	9.00	MW	CG	Z
0.375	9.53	10067	1.06	27.0	.321	8.2	1.4	.24	.63	16	.88	3.9	.43	11.0	0.027	0.7	15.0	MW	C	Z
0.375	9.53	GG-92	1.06	27.0	.307	7.8	7.7	1.3	.52	13	3.9	18	.29	7.3	0.034	0.9	7.50	SST	C	N
0.375	9.53	Z-48	1.06	27.0	.297	7.5	12	2.0	.52	13	6.1	27	.37	9.4	0.039	1.0	9.50	SPR	CG	GI
0.375	9.53	2542	1.06	27.0	.285	7.2	23	4.1	.39	10	9.2	41	.41	10.3	0.045	1.1	9.00	SPR	CG	Z
0.375	9.53	10038	1.06	27.0	.281	7.1	25	4.4	.42	11	10	47	.52	13.1	0.047	1.2	10.0	SPR	C	Z
0.375	9.53	B11-61	1.09	27.8	.325	8.3	3.3	.57	.72	18	2.4	11	.18	4.4	0.025	0.6	6.00	MW	C	Z
0.375	9.53	11871	1.09	27.8	.323	8.2	1.2	.22	.73	19	.91	4.0	.36	9.2	0.026	0.7	13.0	SST	C	N
0.375	9.53	A10-70	1.09	27.8	.265	6.7	50	8.8	.31	7.8	15	69	.55	14.0	0.055	1.4	10.0	SPR	CG	Z
0.375	9.53	S-913	1.09	27.8	.249	6.3	84	15	.26	6.5	22	96	.61	15.6	0.063	1.6	9.75	SST	CG	N
0.375	9.53	S-3039	1.13	28.6	.327	8.3	.66	.12	.71	18	.47	2.1	.42	10.7	0.024	0.6	16.5	SST	C	N
0.375	9.53	B11-22	1.13	28.6	.315	8.0	3.5	.62	.80	20	2.8	13	.33	8.4	0.030	0.8	10.0	MW	C	N
0.375	9.53	U-3	1.13	28.6	.309	7.8	5.3	.93	.73	19	3.9	17	.36	9.2	0.033	0.8	10.0	SPR	C	Z
0.375	9.53	11755	1.13	28.6	.307	7.8	7.5	1.3	.57	14	4.2	19	.29	7.3	0.034	0.9	8.50	SPR	CG	Z
0.375	9.53	519	1.13	28.6	.293	7.4	13	2.3	.53	14	7.0	31	.46	11.7	0.041	1.0	10.3	HD	C	Z
0.375	9.53	F-44	1.13	28.6	.285	7.2	21	3.6	.45	11	9.2	41	.50	12.6	0.045	1.1	10.0	SPR	C	Z
0.375	9.53	10078	1.13	28.6	.279	7.1	26	4.5	.43	11	11	50	.50	12.8	0.048	1.2	10.5	SPR	CG	Z
0.375	9.53	FF-90	1.13	28.6	.265	6.7	44	7.6	.33	8.5	15	65	.55	14.0	0.055	1.4	10.0	SST	CG	N
0.375	9.53	N-111	1.13	28.6	.251	6.4	75	13	.27	6.9	21	92	.62	15.7	0.062	1.6	10.0	SST	CG	N
0.375	9.53	501	1.13	28.6	.231	5.9	154	27	.21	5.2	32	142	.86	21.9	0.072	1.8	11.0	HD	C	Z
0.375	9.53	S-851	1.16	29.4	.319	8.1	1.3	.22	.70	18	.90	4.0	.46	11.6	0.028	0.7	16.3	SST	CG	N
0.375	9.53	HH-44	1.19	30.2	.315	8.0	3.5	.62	.86	22	3.0	14	.33	8.4	0.030	0.8	10.0	MW	C	N
0.375	9.53	2661	1.19	30.2	.293	7.4	11	1.9	.64	16	7.0	31	.49	12.5	0.041	1.0	12.0	SPR	CG	GI
0.375	9.53	II-55	1.19	30.2	.277	7.0	19	3.3	.55	14	10	46	.64	16.2	0.049	1.2	13.0	SST	CG	N
0.375	9.53	GG-84	1.19	30.2	.265	6.7	38	6.7												



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.375	9.53	B-11	1.28	32.5	.263	6.7	29	5.1	.33	8.4	9.6	42	.95	24.2	0.056	1.4	17.0	HD	CG	GI
0.375	9.53	V-60	1.31	33.3	.305	7.7	4.3	.76	.86	22	3.7	17	.46	11.6	0.035	0.9	13.0	SST	CG	N
0.375	9.53	10032	1.31	33.3	.285	7.2	15	2.6	.62	16	9.2	41	.63	16.0	0.045	1.1	13.0	SPR	C	Z
0.375	9.53	12400	1.38	34.9	.341	8.7	.22	.04	1.1	28	.24	1.1	.26	6.5	0.017	0.4	14.0	MW	C	N
0.375	9.53	UU-68	1.38	34.9	.327	8.3	.96	.17	1.1	27	1.0	4.5	.31	7.9	0.024	0.6	12.0	SST	C	N
0.375	9.53	3507	1.38	34.9	.315	8.0	3.7	.64	1.1	27	3.9	17	.32	8.2	0.030	0.8	9.75	MW	C	Z
0.375	9.53	S-207	1.38	34.9	.293	7.4	8.6	1.5	.76	19	6.6	29	.57	14.6	0.041	1.0	13.0	SST	C	N
0.375	9.53	S-282	1.38	34.9	.257	6.5	51	8.8	.35	9.0	18	79	.68	17.2	0.059	1.5	11.5	SST	CG	N
0.375	9.53	H-44	1.38	34.9	.247	6.3	68	12	.35	8.9	24	107	.88	22.4	0.064	1.6	13.8	SPR	CG	GI
0.375	9.53	S-1067	1.38	34.9	.231	5.9	142	25	.21	5.3	30	133	.76	19.2	0.072	1.8	10.5	SST	CG	N
0.375	9.53	12712	1.39	35.3	.307	7.8	6.1	1.1	.97	25	5.9	26	.37	9.5	0.034	0.9	10.0	MW	C	N
0.375	9.53	10579	1.41	35.7	.335	8.5	.51	.09	1.1	29	.59	2.6	.26	6.6	0.020	0.5	12.0	MW	C	Z
0.375	9.53	3936	1.41	35.7	.313	8.0	5.4	.95	.82	21	4.5	20	.28	7.1	0.031	0.8	8.00	MW	C	Z
0.375	9.53	N-125	1.44	36.5	.315	8.0	3.1	.54	.88	22	2.7	12	.33	8.4	0.030	0.8	10.0	SST	C	N
0.375	9.53	FF-87	1.44	36.5	.315	8.0	3.8	.66	.72	18	2.7	12	.29	7.2	0.030	0.8	8.50	SST	C	N
0.375	9.53	FF-94	1.44	36.5	.281	7.1	13	2.3	.64	16	8.5	38	.80	20.3	0.047	1.2	17.0	SPR	CG	GI
0.375	9.53	4183	1.50	38.1	.341	8.7	.19	.03	1.2	31	.23	1.0	.28	7.2	0.017	0.4	15.8	MW	C	N
0.375	9.53	111	1.50	38.1	.325	8.3	1.7	.31	1.2	31	2.2	9.6	.26	6.7	0.025	0.6	9.50	MW	C	Z
0.375	9.53	S-1421	1.50	38.1	.321	8.2	3.0	.53	.66	17	2.0	8.9	.22	5.7	0.027	0.7	7.25	SST	C	N
0.375	9.53	30	1.50	38.1	.319	8.1	2.6	.46	1.2	30	3.2	14	.31	7.8	0.028	0.7	10.0	MW	C	Z
0.375	9.53	S-14	1.50	38.1	.317	8.1	2.1	.37	1.1	29	2.4	11	.38	9.6	0.029	0.7	12.0	SST	C	N
0.375	9.53	2551	1.50	38.1	.315	8.0	2.6	.45	1.1	27	2.8	12	.42	10.7	0.030	0.8	13.0	MW	C	Z
0.375	9.53	S-739	1.50	38.1	.311	7.9	3.9	.69	.84	21	3.3	15	.36	9.1	0.032	0.8	10.3	SST	C	N
0.375	9.53	3820	1.50	38.1	.299	7.6	8.2	1.4	.68	17	5.6	25	.44	11.1	0.038	1.0	11.5	SPR	CG	Z
0.375	9.53	G-73	1.50	38.1	.293	7.4	9.7	1.7	.68	17	6.6	29	.49	12.5	0.041	1.0	12.0	SST	CG	N
0.375	9.53	S-744	1.50	38.1	.291	7.4	10	1.8	.69	17	7.1	31	.56	14.1	0.042	1.1	12.3	SST	C	N
0.375	9.53	S-1216	1.50	38.1	.287	7.3	16	2.8	.50	13	8.1	36	.48	12.3	0.044	1.1	10.0	SST	C	N
0.375	9.53	2554	1.50	38.1	.285	7.2	16	2.7	.59	15	9.2	41	.61	15.4	0.045	1.1	12.5	SPR	C	Z
0.375	9.53	J-50	1.50	38.1	.285	7.2	12	2.1	.73	18	8.6	38	.63	16.0	0.045	1.1	14.0	SST	CG	N
0.375	9.53	10001	1.50	38.1	.281	7.1	20	3.5	.73	19	15	65	.61	15.5	0.047	1.2	12.0	MW	C	Z
0.375	9.53	MM-42	1.50	38.1	.275	7.0	24	4.3	.45	11	11	49	.58	14.6	0.050	1.3	11.5	SST	CG	N
0.375	9.53	3712	1.50	38.1	.263	6.7	33	5.9	.49	12	16	73	.84	21.3	0.056	1.4	15.0	SPR	CG	Z
0.375	9.53	YY-56	1.50	38.1	.245	6.2	78	14	.44	11	35	155	.85	21.5	0.065	1.7	13.0	MW	CG	Z
0.375	9.53	B2-46	1.50	38.1	.213	5.4	325	57	.14	3.5	44	197	.77	19.6	0.081	2.1	9.50	SPR	CG	N
0.375	9.53	4268	1.56	39.7	.335	8.5	.49	.09	1.3	33	.63	2.8	.27	6.9	0.020	0.5	12.5	MW	C	BO
0.375	9.53	2650	1.56	39.7	.299	7.6	7.3	1.3	.77	20	5.6	25	.52	13.3	0.038	1.0	12.8	SPR	C	Z
0.375	9.53	L-46	1.56	39.7	.295	7.5	8.5	1.5	.77	20	6.5	29	.58	14.7	0.040	1.0	13.5	SPR	C	N
0.375	9.53	10998	1.56	39.7	.275	7.0	27	4.7	.44	11	12	52	.64	16.2	0.050	1.3	11.8	HD	C	Z
0.375	9.53	10167	1.59	40.5	.319	8.1	2.6	.46	1.3	32	3.3	15	.31	7.8	0.028	0.7	10.0	MW	C	Z
0.375	9.53	UU-59	1.69	42.8	.231	5.9	93	16	.34	8.7	32	142	1.22	31.1	0.072	1.8	17.0	HD	CG	Z
0.375	9.53	S-1442	1.69	42.8	.215	5.5	166	29	.24	6.1	40	178	1.20	30.5	0.080	2.0	14.0	SST	C	N
0.375	9.53	3904	1.75	44.5	.335	8.5	.57	.10	1.5	38	.86	3.8	.24	6.1	0.020	0.5	11.0	MW	C	Z
0.375	9.53	3316	1.75	44.5	.325	8.3	1.0	.18	1.4	34	1.4	6.0	.40	10.2	0.025	0.6	15.0	MW	C	Z
0.375	9.53	TT-63	1.75	44.5	.325	8.3	.84	.15	1.3	33	1.1	4.8	.46	11.7	0.025	0.6	17.5	MW	C	Z
0.375	9.53	525	1.75	44.5	.307	7.8	3.7	.65	1.1	29	4.2	19	.54	13.8	0.034	0.9	15.0	HD	C	Z
0.375	9.53	12480	1.75	44.5	.305	7.7	3.7	.64	1.1	29	4.1	18	.53	13.3	0.035	0.9	15.0	SST	CG	N
0.375	9.53	114	1.75	44.5	.293	7.4	8.2	1.4	.85	22	7.0	31	.67	16.9	0.041	1.0	15.3	HD	C	Z
0.375	9.53	12293	1.75	44.5	.281	7.1	15	2.6	.71	18	10	47	.73	18.5	0.047	1.2	15.5	SPR	CG	GI
0.375	9.53	3037	1.78	45.2	.287	7.3	11	1.9	.79	20	8.6	38	.68	17.3	0.044	1.1	15.5	SPR	CG	GI
0.375	9.53	3941	1.78	45.2	.251	6.4	46	8.1	.47	12	22	97	1.05	26.8	0.062	1.6	17.0	SPR	CG	Z
0.375	9.53	11587	1.81	46.0	.287	7.3	11	2.0	.76	19	8.6	38	.70	17.9	0.044	1.1	15.0	SPR	CG	N
0.375	9.53	CC-94	1.81	46.0	.285	7.2	11	1.9	.79	20	8.6	38	.68	17.1	0.045	1.1	15.0	SST	CG	N
0.375	9.53	4363	1.88	47.6	.281	7.1	19	3.3	.55	14	10	47	.59	14.9	0.047	1.2	12.5	SPR	CG	Z
0.375	9.53	S-1382	2.00	50.8	.335	8.5	.56	.10	1.5	39	.86	3.8	.22	5.6	0.020	0.5	10.0	SST	C	N
0.375	9.53	10192	2.00	50.8	.319	8.1	1.5	.26	1.6	39	2.3	10	.45	11.4	0.028	0.7	16.0	MW	CG	Z
0.375	9.53	10284	2.00	50.8	.315	8.0	2.0	.35	1.5	38	3.0	13	.51	13.0	0.030	0.8	16.0	MW	C	Z
0.375	9.53	S-442	2.00	50.8	.311	7.9	2.0	.36	1.4	36	2.9	13	.58	14.6	0.032	0.8	18.0	SST	CG	N
0.375	9.53	00-91	2.00	50.8	.295	7.5	5.8	1.0	1.1	29	6.5	29	.76	19.3	0.04.					



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F W S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.375	9.53	11733	2.59	65.9	.250	6.4	33	5.7	.69	17	22	100	1.56	39.7	0.063	1.6	24.0	SPR	CG	Z
0.375	9.53	I-48	2.63	66.7	.295	7.5	5.8	1.0	1.1	28	6.5	29	.79	20.1	0.040	1.0	18.8	SPR	C	N
0.375	9.53	11981	2.66	67.5	.295	7.5	6.1	1.1	1.1	27	6.5	29	.76	19.3	0.040	1.0	18.0	SPR	C	Z
0.375	9.53	B2-49	2.75	69.9	.291	7.4	6.4	1.1	1.1	28	7.1	31	.78	19.7	0.042	1.1	18.5	SST	CG	N
0.375	9.53	12537	2.91	73.9	.231	5.9	56	9.7	.57	15	32	142	2.02	51.2	0.072	1.8	27.0	SPR	C	N
0.375	9.53	12201	3.00	76.2	.313	8.0	1.5	.26	2.2	57	3.3	15	.78	19.7	0.031	0.8	24.0	MW	C	Z
0.375	9.53	12257	3.00	76.2	.291	7.4	6.5	1.1	1.2	29	7.5	34	.90	22.9	0.042	1.1	20.5	SPR	C	Z
0.375	9.53	10002	3.00	76.2	.281	7.1	10	1.8	1.0	26	10	47	1.06	26.9	0.047	1.2	21.5	SPR	C	Z
0.375	9.53	B17-177	3.19	81.0	.281	7.1	6.6	1.2	1.6	40	10	47	1.50	38.2	0.047	1.2	32.0	SPR	CG	Z
0.375	9.53	1713	3.34	84.9	.299	7.6	2.7	.47	2.1	53	5.6	25	1.23	31.2	0.038	1.0	31.3	SPR	C	Z
0.375	9.53	10921	3.38	85.7	.273	6.9	11	2.0	1.1	28	12	55	1.43	36.3	0.051	1.3	27.0	SPR	C	Z
0.375	9.53	3134	3.47	88.1	.267	6.8	13	2.4	1.1	28	15	65	1.65	41.8	0.054	1.4	29.5	SPR	C	Z
0.375	9.53	S-1335	3.50	88.9	.313	8.0	1.4	.25	2.1	54	3.0	13	.71	18.1	0.031	0.8	22.0	SST	C	N
0.375	9.53	12007	3.50	88.9	.295	7.5	4.7	.82	1.4	36	6.5	29	.96	24.4	0.040	1.0	23.0	SPR	C	Z
0.375	9.53	2545	3.50	88.9	.263	6.7	16	2.8	1.0	26	16	73	1.72	43.6	0.056	1.4	29.7	SPR	C	Z
0.375	9.53	2947	3.63	92.1	.293	7.4	3.2	.56	2.1	54	6.8	30	1.52	38.5	0.041	1.0	36.0	SPR	C	Z
0.375	9.53	3921	3.75	95.3	.247	6.3	22	3.8	1.1	28	24	107	2.50	63.4	0.064	1.6	39.0	SPR	CG	Z
0.375	9.53	12210	3.75	95.3	.245	6.2	23	4.1	1.1	27	25	111	2.54	64.4	0.065	1.7	39.0	SPR	CG	N
0.375	9.53	4301	3.75	95.3	.231	5.9	40	6.9	.80	20	32	142	2.66	67.7	0.072	1.8	37.0	SPR	CG	Z
0.375	9.53	B4-7	4.00	101.6	.329	8.4	3.7	.65	.53	14	2.0	8.7	.13	3.2	0.023	0.6	4.50	MW	C	N
0.375	9.53	10600	4.00	101.6	.275	7.0	6.2	1.1	1.8	46	11	50	2.20	55.9	0.050	1.3	44.0	SPR	CG	Z
0.375	9.53	10173	4.50	114.3	.275	7.0	6.9	1.2	1.7	43	12	52	2.00	50.8	0.050	1.3	40.0	SPR	CG	Z
0.375	9.53	3103	7.50	190.5	.251	6.4	12	2.0	1.9	48	22	97	3.91	99.2	0.062	1.6	62.0	SPR	C	Z
0.375	9.53	517	9.00	228.6	.281	7.1	2.6	.44	4.2	107	10	47	3.88	98.5	0.047	1.2	81.5	HD	C	Z
0.375	9.53	12649	10.5	266.7	.299	7.6	1.1	.19	5.1	129	5.6	25	2.74	69.5	0.038	1.0	71.0	SPR	O	N
0.375	9.53	508	12.0	304.8	.251	6.4	5.9	1.0	3.7	94	22	97	7.44	189.0	0.062	1.6	119.0	HD	C	Z
0.380	9.65	A12-31	1.00	25.4	.338	8.6	1.1	.19	.82	21	.90	4.0	.18	4.5	0.021	0.5	7.50	MW	C	Z
0.390	9.91	K-73	.25	6.4	.310	7.9	75	13	.08	2.0	5.9	26	.12	3.0	0.040	1.0	3.00	SST	CG	N
0.390	9.91	10472	.31	7.9	.346	8.8	1.2	.22	.13	3.2	.15	68	.19	4.7	0.022	0.6	7.50	MW	C	Z
0.390	9.91	FF-12	.34	8.7	.290	7.4	114	20	.09	2.4	11	47	.19	4.8	0.050	1.3	3.75	SST	CG	N
0.390	9.91	A13-57	.38	9.5	.320	8.1	28	4.8	.15	3.9	4.3	19	.13	3.3	0.035	0.9	3.75	SPR	CG	N
0.390	9.91	DD-61	.38	9.5	.286	7.3	118	21	.10	2.6	12	53	.21	5.3	0.052	1.3	4.00	SST	CG	N
0.390	9.91	DD-79	.41	10.3	.320	8.1	21	3.8	.20	5.0	4.3	19	.15	3.8	0.035	0.9	4.25	SPR	CG	N
0.390	9.91	O-49	.44	11.1	.326	8.3	7.3	1.3	.25	6.2	1.8	8.0	.19	4.9	0.032	0.8	6.00	SST	CG	N
0.390	9.91	MM-30	.44	11.1	.310	7.9	25	4.3	.22	5.5	5.3	24	.22	5.6	0.040	1.0	5.50	SPR	CG	Z
0.390	9.91	10946	.47	11.9	.340	8.6	4.1	.72	.33	8.4	1.4	6.0	.14	3.5	0.025	0.6	4.50	SST	C	N
0.390	9.91	O-77	.50	12.7	.330	8.4	6.2	1.1	.29	7.4	1.8	8.0	.21	5.3	0.030	0.8	6.00	MW	C	N
0.390	9.91	W-8	.50	12.7	.324	8.2	9.4	1.6	.27	6.8	2.5	11	.23	5.9	0.033	0.8	6.00	SPR	C	GI
0.390	9.91	G-79	.50	12.7	.316	8.0	15	2.7	.28	7.1	4.3	19	.22	5.6	0.037	0.9	6.00	SPR	CG	N
0.390	9.91	H-84	.50	12.7	.310	7.9	25	4.4	.24	6.0	5.9	26	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.390	9.91	71283	.50	12.7	.304	7.7	42	7.3	.26	6.6	11	48	.21	5.3	0.043	1.1	4.88	MW	CG	N
0.390	9.91	71283S	.50	12.7	.304	7.7	35	6.2	.21	5.2	7.3	32	.21	5.3	0.043	1.1	4.88	SST	CG	N
0.390	9.91	71298	.50	12.7	.296	7.5	59	10	.24	6.0	14	62	.24	6.0	0.047	1.2	5.00	MW	CG	N
0.390	9.91	71298S	.50	12.7	.296	7.5	50	8.8	.19	4.8	9.5	42	.24	6.0	0.047	1.2	5.00	SST	CG	N
0.390	9.91	S-144	.50	12.7	.220	5.6	920	161	.05	1.3	46	205	.38	9.7	0.085	2.2	4.50	SST	CG	N
0.390	9.91	71284	.56	14.2	.304	7.7	36	6.4	.30	7.5	11	48	.23	5.7	0.043	1.1	5.25	MW	CG	N
0.390	9.91	71284S	.56	14.2	.304	7.7	31	5.4	.24	6.0	7.3	32	.23	5.7	0.043	1.1	5.25	SST	CG	N
0.390	9.91	71299	.56	14.2	.296	7.5	51	9.0	.27	6.9	14	62	.25	6.4	0.047	1.2	5.38	MW	CG	N
0.390	9.91	71299S	.56	14.2	.296	7.5	44	7.6	.22	5.5	9.5	42	.25	6.4	0.047	1.2	5.38	SST	CG	N
0.390	9.91	K-64	.56	14.3	.336	8.5	3.2	.56	.35	8.8	1.1	4.9	.22	5.5	0.027	0.7	7.00	MW	C	Z
0.390	9.91	10331	.59	15.1	.328	8.3	14	2.5	.30	7.6	4.3	19	.12	3.1	0.031	0.8	4.00	MW	CG	Z
0.390	9.91	WW-8	.63	15.9	.360	9.1	.48	.08	.54	14	.26	1.2	.08	2.1	0.015	0.4	4.50	SST	C	N
0.390	9.91	M-84	.63	15.9	.344	8.7	1.4	.24	.44	11	.60	2.7	.18	4.7	0.023	0.6	8.00	MW	C	BO
0.390	9.91	FF-99	.63	15.9	.270	6.9	148	26	.13	3.3	19	85	.39	9.9	0.060	1.5	5.50	SPR	C	N
0.390	9.91	S-47	.63	15.9	.266	6.8	105	18	.19	4.8	20	88	.43	11.0	0.062	1.6	7.00	SST	CG	N
0.390	9.91	71285	.63	16.0	.304	7.7	32	5.6	.34	8.6	11	48	.25	6.3	0.043	1.1	5.75	MW	CG	N
0.390	9.91	71285S	.63	16.0	.304	7.7	27	4.7	.27	6.9	7.3	32	.25	6.3	0.043	1.1	5.75	SST	CG	N
0.390	9.91	71300	.63	16.0	.296	7.5	45	8.0	.31	7.8	14	62	.28	7.0	0.047	1.2	5.88	MW	CG	N
0.390	9.91	71300S	.63	16																



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.390	9.91	NN-47	.81	20.6	.334	8.5	2.8	.49	.57	14	1.6	7.1	.25	6.2	0.028	0.7	7.75	SST	C	N
0.390	9.91	HH-18	.81	20.6	.326	8.3	6.3	1.1	.50	13	3.2	14	.24	6.1	0.032	0.8	6.50	SST	C	N
0.390	9.91	A-91	.88	22.2	.342	8.7	1.6	.28	.66	17	1.1	4.8	.22	5.5	0.024	0.6	8.00	MW	C	N
0.390	9.91	CC-78	.88	22.2	.340	8.6	2.7	.47	.57	14	1.5	6.8	.17	4.3	0.025	0.6	5.75	SST	C	N
0.390	9.91	11448	.88	22.2	.332	8.4	4.8	.84	.50	13	2.4	11	.20	5.2	0.029	0.7	6.00	SST	C	N
0.390	9.91	10919	.88	22.2	.330	8.4	5.5	.97	.47	12	2.6	12	.21	5.3	0.030	0.8	6.00	SST	C	N
0.390	9.91	B10-16	.88	22.2	.322	8.2	14	2.5	.29	7.3	4.1	18	.20	5.2	0.034	0.9	5.00	SPR	C	N
0.390	9.91	H-31	.88	22.2	.320	8.1	6.0	1.0	.56	14	3.4	15	.32	8.0	0.035	0.9	9.00	SST	CG	N
0.390	9.91	3845	.88	22.2	.310	7.9	17	3.0	.37	9.3	6.3	28	.28	7.1	0.040	1.0	7.00	SPR	CG	Z
0.390	9.91	B15-34	.88	22.2	.310	7.9	13	2.2	.47	12	5.9	26	.32	8.1	0.040	1.0	8.00	SST	CG	N
0.390	9.91	AA-44	.88	22.2	.290	7.4	34	5.9	.32	8.0	11	47	.40	10.2	0.050	1.3	8.00	SST	CG	N
0.390	9.91	3781	.88	22.2	.266	6.8	100	18	.21	5.3	21	94	.50	12.6	0.062	1.6	8.00	HD	CG	Z
0.390	9.91	71289	.88	22.4	.304	7.7	22	3.8	.49	13	11	48	.32	8.1	0.043	1.1	7.38	MW	CG	N
0.390	9.91	71289S	.88	22.4	.304	7.7	19	3.2	.39	10	7.3	32	.32	8.1	0.043	1.1	7.38	SST	CG	N
0.390	9.91	71304	.88	22.4	.296	7.5	29	5.0	.49	12	14	62	.38	9.7	0.047	1.2	8.13	MW	CG	N
0.390	9.91	71304S	.88	22.4	.296	7.5	24	4.2	.39	9.9	9.5	42	.38	9.7	0.047	1.2	8.13	SST	CG	N
0.390	9.91	S-1694	.91	23.0	.334	8.5	4.0	.71	.53	13	2.1	9.5	.20	5.0	0.028	0.7	6.00	SST	C	N
0.390	9.91	3576	.91	23.0	.320	8.1	4.7	.82	.48	12	2.2	10	.43	10.9	0.035	0.9	12.3	HD	CG	GI
0.390	9.91	A10-26	.91	23.0	.306	7.8	15	2.6	.45	11	6.8	30	.35	8.8	0.042	1.1	8.25	SST	CG	N
0.390	9.91	BB-8	.94	23.8	.350	8.9	.75	.13	.77	20	.58	2.6	.17	4.2	0.020	0.5	7.25	SST	C	N
0.390	9.91	MM-43	.94	23.8	.230	5.8	395	69	.10	2.7	41	185	.56	14.2	0.080	2.0	7.00	SPR	CG	BO
0.390	9.91	71290	.94	23.9	.304	7.7	20	3.5	.53	14	11	48	.34	8.6	0.043	1.1	7.88	MW	CG	N
0.390	9.91	71290S	.94	23.9	.304	7.7	17	3.0	.43	11	7.3	32	.34	8.6	0.043	1.1	7.88	SST	CG	N
0.390	9.91	71305	.94	23.9	.296	7.5	28	5.0	.49	13	14	62	.38	9.7	0.047	1.2	8.13	MW	CG	N
0.390	9.91	71305S	.94	23.9	.296	7.5	24	4.2	.39	9.9	9.5	42	.38	9.7	0.047	1.2	8.13	SST	CG	N
0.390	9.91	10955	.97	24.6	.344	8.7	1.5	.26	.77	20	1.1	5.1	.20	5.0	0.023	0.6	7.50	MW	C	Z
0.390	9.91	S-912	.97	24.6	.308	7.8	12	2.1	.53	14	6.3	28	.37	9.4	0.041	1.0	9.00	SST	CG	N
0.390	9.91	U-30	.97	24.6	.262	6.7	73	13	.30	7.5	22	97	.66	16.7	0.064	1.6	10.3	SST	CG	N
0.390	9.91	A12-14	.97	24.6	.346	8.8	1.2	.22	.78	20	.96	4.3	.19	4.7	0.022	0.6	7.50	MW	C	Z
0.390	9.91	EE-98	1.00	25.4	.344	8.7	.49	.09	.55	14	.27	1.2	.45	11.4	0.023	0.6	18.5	MW	C	Z
0.390	9.91	A-82	1.00	25.4	.320	8.1	8.8	1.5	.48	12	4.3	19	.30	7.6	0.035	0.9	7.50	SPR	C	Z
0.390	9.91	O-154	1.00	25.4	.308	7.8	13	2.2	.53	14	6.8	30	.43	10.9	0.041	1.0	9.50	SPR	C	GI
0.390	9.91	71291	1.00	25.4	.304	7.7	19	3.3	.58	15	11	48	.35	9.0	0.043	1.1	8.25	MW	CG	N
0.390	9.91	71291S	1.00	25.4	.304	7.7	16	2.8	.46	12	7.3	32	.35	9.0	0.043	1.1	8.25	SST	CG	N
0.390	9.91	71306	1.00	25.4	.296	7.5	27	4.7	.52	13	14	62	.40	10.1	0.047	1.2	8.50	MW	CG	N
0.390	9.91	71306S	1.00	25.4	.296	7.5	23	4.0	.42	11	9.5	42	.40	10.1	0.047	1.2	8.50	SST	CG	N
0.390	9.91	PP-6	1.00	25.4	.290	7.4	24	4.2	.45	11	11	47	.53	13.3	0.050	1.3	10.5	SST	CG	N
0.390	9.91	B9-28	1.00	25.4	.272	6.9	84	15	.22	5.6	18	81	.46	11.6	0.059	1.5	7.75	SPR	CG	Z
0.390	9.91	B10-23	1.06	27.0	.274	7.0	54	9.5	.30	7.7	16	73	.54	13.6	0.058	1.5	9.25	SST	CG	N
0.390	9.91	H-61	1.06	27.0	.262	6.7	99	17	.23	5.9	23	103	.58	14.6	0.064	1.6	9.00	SPR	CG	Z
0.390	9.91	S-1130	1.13	28.6	.360	9.1	.15	.03	.96	24	.14	.64	.17	4.2	0.015	0.4	10.0	SST	C	N
0.390	9.91	4134	1.13	28.6	.260	6.6	107	19	.23	5.8	24	108	.65	16.5	0.065	1.7	9.00	SPR	C	Z
0.390	9.91	71292	1.13	28.7	.304	7.7	17	2.9	.65	17	11	48	.39	10.0	0.043	1.1	9.13	MW	CG	N
0.390	9.91	71292S	1.13	28.7	.304	7.7	14	2.5	.52	13	7.3	32	.39	10.0	0.043	1.1	9.13	SST	CG	N
0.390	9.91	71307	1.13	28.7	.296	7.5	24	4.1	.59	15	14	62	.44	11.2	0.047	1.2	9.38	MW	CG	N
0.390	9.91	71307S	1.13	28.7	.296	7.5	20	3.5	.47	12	9.5	42	.44	11.2	0.047	1.2	9.38	SST	CG	N
0.390	9.91	K-7	1.19	30.2	.316	8.0	7.2	1.3	.65	16	4.7	21	.39	9.9	0.037	0.9	9.50	SST	C	N
0.390	9.91	G-55	1.19	30.2	.308	7.8	9.8	1.7	.65	16	6.3	28	.47	12.0	0.041	1.0	10.5	SST	C	N
0.390	9.91	3243	1.19	30.2	.290	7.4	23	4.1	.48	12	11	50	.64	16.2	0.050	1.3	11.8	SPR	C	Z
0.390	9.91	A-90	1.19	30.2	.262	6.7	103	18	.22	5.7	23	103	.56	14.2	0.064	1.6	8.75	HD	CG	N
0.390	9.91	A10-5	1.22	31.0	.340	8.6	1.9	.33	.82	21	1.5	6.8	.19	4.8	0.025	0.6	7.50	SST	CG	N
0.390	9.91	YY-67	1.25	31.8	.346	8.8	.68	.12	.96	24	.65	2.9	.29	7.3	0.022	0.6	12.0	MW	C	Z
0.390	9.91	B4-19	1.25	31.8	.344	8.7	1.1	.20	1.0	26	1.1	5.1	.24	6.0	0.023	0.6	9.25	MW	C	N
0.390	9.91	71293	1.25	31.8	.304	7.7	15	2.6	.73	19	11	48	.43	10.9	0.043	1.1	10.0	MW	CG	N
0.390	9.91	71293S	1.25	31.8	.304	7.7	13	2.2	.58	15	7.3	32	.43	10.9	0.043	1.1	10.0	SST	CG	N
0.390	9.91	71308	1.25	31.8	.296	7.5	21	3.6	.67	17	14	62	.49	12.4	0.047	1.2	10.4	MW	CG	N
0.390	9.91	71308S	1.25	31.8	.296	7.5	18	3.1	.54	14	9.5	42	.49	12.4	0.047	1.2	10.4	SST	CG	N
0.390	9.91	S-304	1.25	31.8	.266	6.8	43	7.5	.35	8.9	15	67	.90	22.8	0.062	1.6	14.5	SST	CG	N
0.390	9.91	3002</																		



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.390	9.91	L-34	1.75	44.5	.350	8.9	.33	.06	1.4	36	.46	2.1	.34	8.6	0.020	0.5	16.0	MW	C	Z
0.390	9.91	BB-76	1.75	44.5	.346	8.8	.53	.09	1.4	37	.77	3.4	.31	7.8	0.022	0.6	13.0	SST	C	N
0.390	9.91	71296	1.75	44.5	.304	7.7	10	1.8	1.0	26	11	48	.57	14.5	0.043	1.1	13.3	MW	CG	N
0.390	9.91	71296S	1.75	44.5	.304	7.7	8.9	1.6	.82	21	7.3	32	.57	14.5	0.043	1.1	13.3	SST	CG	N
0.390	9.91	71311	1.75	44.5	.296	7.5	15	2.5	.96	24	14	62	.66	16.7	0.047	1.2	14.0	MW	CG	N
0.390	9.91	71311S	1.75	44.5	.296	7.5	12	2.2	.77	19	9.5	42	.66	16.7	0.047	1.2	14.0	SST	CG	N
0.390	9.91	2922	1.81	46.0	.348	8.8	.40	.07	1.5	37	.58	2.6	.36	9.1	0.021	0.5	16.0	MW	C	Z
0.390	9.91	H-86	1.88	47.6	.350	8.9	.35	.06	1.6	39	.54	2.4	.32	8.1	0.020	0.5	15.0	MW	C	Z
0.390	9.91	3314	1.88	47.6	.296	7.5	17	3.0	.58	15	10	45	.61	15.5	0.047	1.2	12.0	HD	C	Z
0.390	9.91	TT-29	1.88	47.6	.290	7.4	14	2.5	.75	19	11	47	.80	20.3	0.050	1.3	16.0	SST	CG	N
0.390	9.91	I-50	1.88	47.6	.276	7.0	28	5.0	.58	15	17	74	.94	23.9	0.057	1.4	16.5	SPR	CG	GI
0.390	9.91	10086	2.00	50.8	.310	7.9	5.1	.90	1.2	31	6.3	28	.75	19.1	0.040	1.0	18.8	SPR	CG	N
0.390	9.91	2607	2.00	50.8	.308	7.8	6.4	1.1	1.3	32	8.0	36	.74	18.7	0.041	1.0	17.0	MW	C	GI
0.390	9.91	71297	2.00	50.8	.304	7.7	9.8	1.7	1.1	28	11	48	.60	15.3	0.043	1.1	14.0	MW	CG	N
0.390	9.91	71297S	2.00	50.8	.304	7.7	8.3	1.5	.88	22	7.3	32	.60	15.3	0.043	1.1	14.0	SST	CG	N
0.390	9.91	71312	2.00	50.8	.296	7.5	13	2.2	1.1	28	14	62	.74	18.8	0.047	1.2	15.8	MW	CG	N
0.390	9.91	71312S	2.00	50.8	.296	7.5	11	1.9	.88	22	9.5	42	.74	18.8	0.047	1.2	15.8	SST	CG	N
0.390	9.91	2764	2.00	50.8	.296	7.5	9.7	1.7	1.0	27	10	45	.94	23.9	0.047	1.2	20.0	HD	CG	Z
0.390	9.91	2943	2.03	51.6	.338	8.6	1.5	.27	1.7	43	2.6	11	.29	7.3	0.026	0.7	11.0	MW	CG	Z
0.390	9.91	2883	2.13	54.0	.296	7.5	11	1.9	.95	24	10	45	.86	21.9	0.047	1.2	18.3	SPR	CG	Z
0.390	9.91	GG-86	2.25	57.2	.326	8.3	2.0	.36	1.6	40	3.2	14	.54	13.8	0.032	0.8	16.0	SST	C	N
0.390	9.91	EE-96	2.50	63.5	.210	5.3	184	32	.30	7.6	55	246	1.89	48.0	0.090	2.3	21.0	SPR	CG	N
0.390	9.91	11396	2.69	68.2	.282	7.2	17	3.0	.83	21	14	63	1.19	30.2	0.054	1.4	21.0	HD	C	Z
0.390	9.91	S-1337	3.25	82.6	.288	7.3	10	1.8	1.1	28	11	50	1.25	31.7	0.051	1.3	23.5	SST	C	N
0.390	9.91	3392	3.38	85.7	.298	7.6	7.5	1.3	1.3	32	9.5	42	1.10	28.0	0.046	1.2	23.0	SPR	C	Z
0.390	9.91	10901	3.50	88.9	.314	8.0	3.8	.67	1.4	36	5.4	24	.76	19.3	0.038	1.0	20.0	SPR	CG	N
0.390	9.91	11465	4.75	120.7	.326	8.3	1.24	.218	2.55	64.77	3.16	14.12	.83	21.1	0.032	0.8	25.0	SST	C	N
0.406	10.31	BB-78	.38	9.5	.368	9.3	.94	.16	.28	7.1	.26	1.2	.10	2.4	0.019	0.5	5.00	SST	C	N
0.406	10.31	B-62	.38	9.5	.336	8.5	21	3.7	.19	4.9	4.1	18	.14	3.6	0.035	0.9	4.00	SPR	CG	Z
0.406	10.31	12533	.41	10.3	.370	9.4	1.5	.26	.33	8.3	.49	2.2	.08	2.1	0.018	0.5	3.50	SST	C	N
0.406	10.31	J-41	.41	10.3	.370	9.4	.86	.15	.30	7.6	.26	1.1	.11	2.7	0.018	0.5	5.00	MW	C	N
0.406	10.31	A-66	.41	10.3	.348	8.8	6.3	1.1	.26	6.6	1.7	7.3	.15	3.7	0.029	0.7	5.00	MW	CG	N
0.406	10.31	M-24	.41	10.3	.306	7.8	72	13	.15	3.8	11	48	.24	6.0	0.050	1.3	4.75	SPR	CG	N
0.406	10.31	S-1096	.44	11.1	.356	9.0	2.2	.39	.26	6.7	.58	2.6	.18	4.4	0.025	0.6	6.00	SST	C	N
0.406	10.31	W-28	.44	11.1	.350	8.9	7.3	1.3	.28	7.2	2.1	9.2	.14	3.6	0.028	0.7	4.00	SST	C	N
0.406	10.31	BB-42	.44	11.1	.306	7.8	66	12	.16	4.2	11	48	.25	6.4	0.050	1.3	5.00	SPR	CG	N
0.406	10.31	JJ-12	.50	12.7	.358	9.1	1.9	.33	.36	9.0	.66	2.9	.14	3.7	0.024	0.6	6.00	SST	CG	N
0.406	10.31	EE-89	.50	12.7	.348	8.8	6.3	1.1	.33	8.3	2.1	9.2	.17	4.4	0.029	0.7	5.00	MW	C	Z
0.406	10.31	N-63	.50	12.7	.334	8.5	16	2.8	.28	7.1	4.4	20	.18	4.6	0.036	0.9	5.00	SPR	CG	Z
0.406	10.31	A10-55	.50	12.7	.332	8.4	15	2.7	.30	7.5	4.5	20	.20	5.2	0.037	0.9	5.50	SPR	CG	N
0.406	10.31	GG-69	.50	12.7	.326	8.3	25	4.4	.24	6.2	6.1	27	.20	5.1	0.040	1.0	5.00	SPR	CG	Z
0.406	10.31	K-95	.50	12.7	.282	7.2	161	28	.13	3.2	20	91	.33	8.3	0.062	1.6	5.25	HD	CG	Z
0.406	10.31	J-17	.50	12.7	.272	6.9	297	52	.09	2.2	25	113	.30	7.7	0.067	1.7	4.50	SPR	CG	GI
0.406	10.31	I-98	.50	12.7	.242	6.1	678	119	.06	1.5	40	179	.37	9.4	0.082	2.1	4.50	SST	CG	N
0.406	10.31	B7-22	.53	13.5	.328	8.3	27	4.7	.21	5.3	5.6	25	.18	4.5	0.039	1.0	4.50	SPR	CG	Z
0.406	10.31	10843	.53	13.5	.278	7.1	172	30	.13	3.3	22	99	.35	8.9	0.064	1.6	5.50	SPR	CG	N
0.406	10.31	3629	.53	13.5	.232	5.9	846	148	.06	1.5	51	226	.44	11.0	0.087	2.2	5.00	SPR	CG	GI
0.406	10.31	A12-13	.54	13.7	.364	9.2	2.1	.37	.43	11	.92	4.1	.11	2.7	0.021	0.5	4.00	SST	C	N
0.406	10.31	B11-32	.56	14.3	.360	9.1	1.8	.31	.42	11	.76	3.4	.14	3.5	0.023	0.6	6.00	MW	CG	N
0.406	10.31	H-1	.56	14.3	.354	9.0	2.6	.46	.38	9.7	.99	4.4	.18	4.6	0.026	0.7	6.00	SST	C	N
0.406	10.31	XX-35	.56	14.3	.352	8.9	4.9	.85	.38	9.6	1.8	8.2	.15	3.8	0.027	0.7	4.50	SST	C	N
0.406	10.31	XX-47	.56	14.3	.350	8.9	3.3	.57	.34	8.6	1.1	4.9	.22	5.7	0.028	0.7	7.00	MW	C	Z
0.406	10.31	00-45	.56	14.3	.346	8.8	4.4	.77	.35	8.9	1.5	6.9	.21	5.3	0.030	0.8	7.00	MW	CG	N
0.406	10.31	3718	.56	14.3	.324	8.2	17	2.9	.28	7.0	4.6	20	.29	7.3	0.041	1.0	7.00	SPR	CG	Z
0.406	10.31	J-4	.56	14.3	.316	8.0	56	9.8	.15	3.9	8.6	38	.19	4.9	0.045	1.1	4.25	SPR	CG	Z
0.406	10.31	I-55	.59	15.1	.358	9.1	1.4	.25	.38	9.6	.54	2.4	.22	5.5	0.024	0.6	8.00	MW	C	BO
0.406	10.31	A-2	.59	15.1	.358	9.1	1.4	.25	.40	10	.57	2.5	.19	4.9	0.024	0.6	8.00	MW	CG	N
0.406	10.31	S-1480	.59	15.1	.350	8.9	4.7	.83	.43	11	2.0	9.0	.17	4.3	0.028	0.7	5.00	SST	C	N
0.406	10.31	O-2	.59	15.1	.346	8.8	5.5	.96	.41	10	2.3									



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.406	10.31	4327	.75	19.1	.282	7.2	116	20	.18	4.5	20	91	.40	10.2	0.062	1.6	6.50	SPR	CG	Z
0.406	10.31	K-81	.75	19.1	.278	7.1	151	26	.15	3.8	22	99	.38	9.8	0.064	1.6	6.00	SPR	CG	N
0.406	10.31	A12-27	.80	20.3	.364	9.2	.49	.09	.53	13	.26	1.1	.27	6.9	0.021	0.5	12.0	MW	C	N
0.406	10.31	10811	.81	20.6	.382	9.7	.09	.02	.72	18	.06	.28	.10	2.4	0.012	0.3	7.00	SST	C	N
0.406	10.31	S-1323	.81	20.6	.370	9.4	.28	.05	.63	16	.18	.79	.18	4.6	0.018	0.5	10.0	SST	CG	N
0.406	10.31	10155	.81	20.6	.366	9.3	.53	.09	.60	15	.32	1.4	.21	5.3	0.020	0.5	9.50	MW	C	Z
0.406	10.31	A-53	.81	20.6	.324	8.2	15	2.7	.43	11	6.5	29	.31	7.8	0.041	1.0	7.50	SPR	CG	GI
0.406	10.31	A10-30	.81	20.6	.304	7.7	35	6.1	.33	8.4	12	51	.42	10.7	0.051	1.3	8.25	SPR	CG	GI
0.406	10.31	N-49	.81	20.6	.286	7.3	78	14	.22	5.7	17	78	.42	10.7	0.060	1.5	7.00	SST	CG	N
0.406	10.31	PP-96	.81	20.6	.286	7.3	62	11	.26	6.5	16	71	.56	14.1	0.060	1.5	9.25	SPR	CG	Z
0.406	10.31	2865	.88	22.2	.382	9.7	.07	.01	.76	19	.05	.23	.12	3.0	0.012	0.3	9.00	MW	C	Z
0.406	10.31	1559	.88	22.2	.364	9.2	.78	.14	.68	17	.53	2.4	.19	4.9	0.021	0.5	8.25	MW	C	Z
0.406	10.31	V-52	.88	22.2	.356	9.0	1.3	.22	.63	16	.79	3.5	.25	6.4	0.025	0.6	9.00	SST	C	N
0.406	10.31	10125	.88	22.2	.336	8.5	11	1.8	.39	9.8	4.1	18	.25	6.2	0.035	0.9	6.00	SPR	C	GI
0.406	10.31	PP-73	.88	22.2	.326	8.3	11	1.9	.51	13	5.7	25	.32	8.1	0.040	1.0	8.00	SST	CG	N
0.406	10.31	GG-82	.88	22.2	.324	8.2	10	1.8	.51	13	5.3	23	.37	9.4	0.041	1.0	9.00	SST	CG	N
0.406	10.31	I-96	.88	22.2	.310	7.9	24	4.2	.44	11	10	46	.43	11.0	0.048	1.2	9.00	SPR	CG	Z
0.406	10.31	GG-90	.88	22.2	.288	7.3	66	12	.25	6.4	17	74	.50	12.7	0.059	1.5	7.50	SST	C	N
0.406	10.31	S-134	.88	22.2	.262	6.7	150	26	.19	4.7	28	124	.58	14.6	0.072	1.8	8.00	SST	CG	N
0.406	10.31	3745	.88	22.2	.246	6.2	283	50	.14	3.6	40	179	.64	16.3	0.080	2.0	8.00	SPR	CG	Z
0.406	10.31	10539	.91	23.0	.322	8.2	14	2.4	.48	12	6.6	29	.34	8.5	0.042	1.1	8.00	SST	CG	N
0.406	10.31	1545	.94	23.8	.362	9.2	1.0	.18	.74	19	.74	3.3	.20	5.0	0.022	0.6	8.00	MW	C	Z
0.406	10.31	U-11	.94	23.8	.354	9.0	1.7	.30	.70	18	1.2	5.4	.23	5.9	0.026	0.7	8.00	SST	C	N
0.406	10.31	B-4	.94	23.8	.330	8.4	8.6	1.5	.60	15	5.1	23	.34	8.7	0.038	1.0	9.00	HD	CG	Z
0.406	10.31	2863	.94	23.8	.324	8.2	19	3.3	.35	8.9	6.5	29	.31	7.8	0.041	1.0	6.50	SPR	C	Z
0.406	10.31	L-58	.94	23.8	.302	7.7	39	6.9	.31	7.9	12	54	.42	10.6	0.052	1.3	8.00	SPR	CG	Z
0.406	10.31	G-64	.97	24.6	.356	9.0	1.5	.26	.74	19	1.1	5.0	.23	5.7	0.025	0.6	8.00	SST	C	N
0.406	10.31	W-3	.97	24.6	.344	8.7	4.5	.78	.62	16	2.8	12	.22	5.5	0.031	0.8	7.00	SST	CG	N
0.406	10.31	10963	.98	25.0	.262	6.7	230	40	.13	3.3	30	132	.54	13.7	0.072	1.8	6.50	HD	C	Z
0.406	10.31	U-86	1.00	25.4	.372	9.4	.26	.05	.85	22	.22	.97	.15	3.9	0.017	0.4	9.00	SST	CG	N
0.406	10.31	S-1152	1.00	25.4	.368	9.3	.70	.12	.87	22	.61	2.7	.13	3.4	0.019	0.5	6.00	SST	C	N
0.406	10.31	S-265	1.00	25.4	.362	9.2	1.1	.20	.84	21	.96	4.3	.17	4.2	0.022	0.6	6.50	SST	C	N
0.406	10.31	S-477	1.00	25.4	.358	9.1	.46	.08	.54	14	.25	1.1	.46	11.6	0.024	0.6	18.0	SST	C	N
0.406	10.31	S-1046	1.00	25.4	.354	9.0	.65	.11	.51	13	.33	1.5	.49	12.5	0.026	0.7	18.0	SST	C	N
0.406	10.31	V-65	1.00	25.4	.342	8.7	3.6	.63	.68	17	2.4	11	.32	8.1	0.032	0.8	9.00	SST	C	N
0.406	10.31	3607	1.00	25.4	.338	8.6	7.5	1.3	.73	18	5.4	24	.27	6.9	0.034	0.9	7.00	MW	C	GI
0.406	10.31	3624	1.00	25.4	.326	8.3	10	1.8	.61	15	6.1	27	.38	9.7	0.040	1.0	9.50	SPR	CG	Z
0.406	10.31	3919	1.00	25.4	.322	8.2	11	1.9	.56	14	6.1	27	.44	11.2	0.042	1.1	10.5	SPR	CG	Z
0.406	10.31	941	1.00	25.4	.306	7.8	28	5.0	.50	13	14	63	.50	12.7	0.050	1.3	9.00	MW	C	Z
0.406	10.31	A-49	1.00	25.4	.282	7.2	95	17	.21	5.5	20	91	.53	13.4	0.062	1.6	7.50	SPR	C	Z
0.406	10.31	3901	1.00	25.4	.278	7.1	67	12	.30	7.5	20	88	.70	17.9	0.064	1.6	11.0	SPR	CG	Z
0.406	10.31	Q0-39	1.00	25.4	.278	7.1	93	16	.33	8.5	31	138	.54	13.8	0.064	1.6	8.50	MW	CG	Z
0.406	10.31	EE-55	1.03	26.2	.306	7.8	27	4.8	.40	10	11	48	.46	11.7	0.050	1.3	9.25	SPR	CG	N
0.406	10.31	M-108	1.06	27.0	.356	9.0	1.1	.19	.81	21	.90	4.0	.25	6.4	0.025	0.6	10.0	SST	CG	N
0.406	10.31	JJ-96	1.06	27.0	.342	8.7	5.8	1.0	.57	14	3.3	15	.26	6.5	0.032	0.8	7.00	HD	C	GI
0.406	10.31	3794	1.06	27.0	.312	7.9	22	3.8	.45	11	9.7	43	.42	10.7	0.047	1.2	9.00	SPR	CG	Z
0.406	10.31	H-41	1.06	27.0	.298	7.6	28	4.9	.46	12	13	57	.58	14.7	0.054	1.4	10.8	SST	CG	N
0.406	10.31	3696	1.06	27.0	.282	7.2	75	13	.27	6.9	20	91	.56	14.2	0.062	1.6	9.00	SPR	CG	Z
0.406	10.31	S-119	1.06	27.0	.262	6.7	167	29	.17	4.2	28	124	.61	15.5	0.072	1.8	7.50	SST	C	N
0.406	10.31	B8-50	1.09	27.8	.338	8.6	5.3	.93	.74	19	3.9	17	.34	8.6	0.034	0.9	9.00	SPR	C	N
0.406	10.31	O-57	1.09	27.8	.328	8.3	11	2.0	.50	13	5.6	25	.31	7.9	0.039	1.0	8.00	SPR	CG	GI
0.406	10.31	B12-31	1.13	28.6	.356	9.0	.66	.11	.69	17	.45	2.0	.44	11.1	0.025	0.6	17.5	MW	CG	N
0.406	10.31	3508	1.13	28.6	.332	8.4	7.4	1.3	.65	17	4.8	21	.38	9.6	0.037	0.9	9.25	HD	C	Z
0.406	10.31	N-117	1.13	28.6	.236	6.0	324	57	.15	3.7	48	212	.77	19.4	0.085	2.2	9.00	SPR	CG	N
0.406	10.31	FF-84	1.19	30.2	.336	8.5	6.0	1.1	.68	17	4.1	18	.35	8.9	0.035	0.9	9.00	SPR	C	N
0.406	10.31	FF-40	1.19	30.2	.326	8.3	6.7	1.2	.71	18	4.7	21	.48	12.2	0.040	1.0	12.0	SST	CG	N
0.406	10.31	3766	1.19	30.2	.324	8.2	20	3.4	.33	8.4	6.5	29	.30	7.6	0.041	1.0	6.25	SPR	C	GI
0.406	10.31	A15-46	1.19	30.2	.306	7.8	22	3.9	.49	12	11	48	.54	13.8	0.050	1.3	11.0	SPR	CG	N
0.406	10.31	S-1682	1.20	30.6	.368	9.3	.30	.05	.97	25	.29	1.3	.24	6.0	0.019	0.5	11.5	SST	C	N
0.406	10.31	Y-35	1.25	31.8	.356	9.0	1.2	.21	.96	24	1.1	5.1	.29	7.3	0.025	0.6	10.5	MW	C	N
0.406	10.31	A12-16	1.25	31.8	.330	8.4	6.7	1.2	.79	20	5.3	24	.46	11.6	0.038	1.0	11.0	MW	C	N
0.406	10.31	B11-70	1.25	31.8	.326	8.3	11	1.9	.57	14	6.1	27	.36	9.1	0.040	1.0	9.00	SPR	CG	N
0.406	10.31	3538	1.28	32.5	.336	8.5	5.6	.99	.73	18	4.1	18	.33	8.4	0.035	0.9	9.50	HD	CG	Z
0.406	10.31	12530	1.31	33.3	.330	8.4	7.1	1.2	.88	22	6.2	28	.44	11.1	0.038	1.0	10.5	MW	C	N
0.406	10.31	B2-67	1.31	33.3	.330	8.4	7.1	1.2	.88	22	6.2	28	.44	11.1	0.038	1.0	10.5	MW	CL	N
0.406	10.31	I-39	1.31	33.3	.304	7.7	21	3.7	.54	14	12	51	.62	15.9	0.051	1.3	12.3	SPR	CG	Z
0.406	10.31	V-33	1.31	33.3	.282	7.2	45	7.9	.42	11	19	85	.74	18.9	0.062	1.6	12.0	SST	CG	N
0.406	10.31	A9-45	1.34	34.1	.322	8.2	7.3	1.3	.72	18	5.3	23	.62	15.7	0.042	1.1	14.8	SPR	CG	Z
0.406	10.31	Z-62	1.38	34.9	.322	8.2	12	2.0	.60	15	7.0	31	.42	1						




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.406	10.31	FF-76	1.75	44.5	.346	8.8	3.1	.55	1.2	31	3.8	17	.27	6.9	0.030	0.8	9.00	MW	CG	N
0.406	10.31	NN-44	1.75	44.5	.346	8.8	1.7	.30	1.3	32	2.1	9.5	.48	12.2	0.030	0.8	15.0	MW	C	Z
0.406	10.31	S-935	1.75	44.5	.324	8.2	6.3	1.1	.97	25	6.1	27	.56	14.3	0.041	1.0	13.8	SST	CG	N
0.406	10.31	8	1.75	44.5	.282	7.2	37	6.5	.55	14	20	91	.99	25.2	0.062	1.6	16.0	HD	CG	Z
0.406	10.31	FF-88	1.75	44.5	.186	4.7	738	129	.12	3.1	89	396	1.43	36.3	0.110	2.8	13.0	SPR	CG	N
0.406	10.31	11131	1.78	45.2	.342	8.7	3.4	.59	1.3	34	4.6	20	.37	9.3	0.032	0.8	10.5	MW	CG	Z
0.406	10.31	NN-53	1.78	45.2	.306	7.8	12	2.2	.88	22	11	48	.90	22.9	0.050	1.3	18.0	SPR	C	Z
0.406	10.31	2860	1.78	45.2	.298	7.6	21	3.6	.92	23	19	84	.84	21.4	0.054	1.4	15.5	MW	CG	Z
0.406	10.31	12235	1.78	45.2	.284	7.2	44	7.7	.44	11	19	87	.79	20.1	0.061	1.5	13.0	SPR	CG	Z
0.406	10.31	GG-58	1.88	47.6	.346	8.8	1.7	.30	1.4	36	2.4	11	.45	11.4	0.030	0.8	15.0	MW	CG	N
0.406	10.31	10533	1.88	47.6	.294	7.5	21	3.7	.72	18	15	68	1.05	26.7	0.056	1.4	17.8	SPR	C	Z
0.406	10.31	12735	1.91	48.5	.302	7.7	24	4.1	.52	13	12	54	.68	17.2	0.052	1.3	12.0	SPR	C	N
0.406	10.31	3646	2.00	50.8	.336	8.5	3.8	.67	1.5	37	5.7	25	.49	12.4	0.035	0.9	13.0	MW	C	GI
0.406	10.31	11443	2.00	50.8	.322	8.2	6.2	1.1	1.1	29	7.0	31	.76	19.2	0.042	1.1	17.0	HD	C	Z
0.406	10.31	115	2.00	50.8	.312	7.9	10	1.8	.95	24	9.7	43	.83	21.2	0.047	1.2	16.8	HD	C	Z
0.406	10.31	10873	2.03	51.6	.294	7.5	22	3.8	.65	17	14	64	.86	21.8	0.056	1.4	15.3	SST	CG	N
0.406	10.31	A9-30	2.06	52.4	.310	7.9	9.2	1.6	1.1	28	10	45	.96	24.4	0.048	1.2	20.0	SPR	CG	GI
0.406	10.31	3602	2.13	54.0	.312	7.9	8.4	1.5	1.2	29	9.7	43	.94	23.9	0.047	1.2	20.0	HD	CG	GI
0.406	10.31	3574	2.31	58.7	.314	8.0	8.6	1.5	1.1	27	9.1	41	.83	21.0	0.046	1.2	18.0	HD	CG	Z
0.406	10.31	B14-40	2.34	59.5	.274	7.0	39	6.8	.63	16	24	109	1.39	35.2	0.066	1.7	20.0	SPR	C	Z
0.406	10.31	4220	2.38	60.3	.346	8.8	1.7	.30	1.9	48	3.2	14	.48	12.2	0.030	0.8	15.0	MW	C	Z
0.406	10.31	4176	2.38	60.3	.308	7.8	12	2.1	.91	23	11	49	.88	22.4	0.049	1.2	17.0	SPR	C	Z
0.406	10.31	EE-93	2.38	60.3	.306	7.8	12	2.2	.88	22	11	48	.90	22.9	0.050	1.3	18.0	SPR	CG	Z
0.406	10.31	2507	2.44	61.9	.250	6.4	77	14	.68	17	52	232	1.76	44.6	0.078	2.0	21.5	MW	C	Z
0.406	10.31	11415	2.50	63.5	.312	7.9	7.2	1.3	1.3	34	9.7	43	1.13	28.7	0.047	1.2	23.0	HD	C	Z
0.406	10.31	11307	2.50	63.5	.306	7.8	9.7	1.7	1.1	27	10	46	1.01	25.7	0.050	1.3	20.3	SST	CG	N
0.406	10.31	4261	2.56	65.1	.344	8.7	1.4	.24	1.9	48	2.6	11	.67	16.9	0.031	0.8	20.5	MW	CG	Z
0.406	10.31	11480	2.59	65.9	.346	8.8	1.7	.30	2.1	54	3.6	16	.48	12.2	0.030	0.8	15.0	MW	CG	Z
0.406	10.31	4216	2.75	69.9	.344	8.7	1.6	.28	2.2	55	3.4	15	.59	15.0	0.031	0.8	18.0	MW	C	Z
0.406	10.31	22	2.75	69.9	.312	7.9	7.3	1.3	1.3	34	9.7	43	1.12	28.3	0.047	1.2	22.8	HD	C	Z
0.406	10.31	1914	2.81	71.4	.312	7.9	8.7	1.5	1.1	29	9.7	43	.96	24.5	0.047	1.2	19.5	SPR	C	Z
0.406	10.31	LL-99	3.25	82.6	.282	7.2	22	3.8	.94	24	20	91	1.61	40.9	0.062	1.6	26.0	SPR	CG	N
0.406	10.31	10575	3.31	84.1	.262	6.7	37	6.5	.80	20	30	132	2.16	54.9	0.072	1.8	30.0	SPR	CG	Z
0.406	10.31	10699	4.00	101.6	.332	8.4	2.3	.40	2.1	54	4.8	21	.94	24.0	0.037	0.9	25.5	SPR	CG	Z
0.406	10.31	3613	4.25	108.0	.322	8.2	3.3	.58	2.9	74	9.7	43	1.26	32.0	0.042	1.1	30.0	MW	CG	Z
0.406	10.31	3802	4.38	111.1	.316	8.0	3.8	.66	2.3	57	8.6	38	1.62	41.1	0.045	1.1	35.0	SPR	C	Z
0.406	10.31	11948	4.38	111.1	.306	7.8	6.0	1.1	1.8	46	11	48	1.75	44.5	0.050	1.3	35.0	SPR	CG	GI
0.406	10.31	10380	7.25	184.2	.262	6.7	21	3.6	1.4	36	30	132	3.74	95.1	0.072	1.8	52.0	SPR	CG	Z
0.406	10.31	11833	8.25	209.6	.256	6.5	20	3.5	1.6	40	31	139	4.37	111.0	0.075	1.9	57.3	SST	C	N
0.406	10.31	10908	8.50	215.9	.260	6.6	23	4.0	1.4	35	31	138	3.72	94.6	0.073	1.9	51.0	SPR	CG	N
0.410	10.41	12683	2.75	69.9	.310	7.9	15	2.7	.97	25	15	67	.78	19.7	0.050	1.3	14.5	MW	C	N
0.420	10.67	H-25	.28	7.1	.338	8.6	74	13	.09	2.2	6.3	28	.12	3.1	0.041	1.0	3.00	SPR	CG	N
0.420	10.67	K-83	.31	7.9	.340	8.6	59	10	.09	2.4	5.5	24	.12	3.0	0.040	1.0	3.00	SST	CG	N
0.420	10.67	B10-50	.31	7.9	.340	8.6	67	12	.09	2.2	5.9	26	.16	4.1	0.040	1.0	3.00	SPR	C	N
0.420	10.67	JJ-92	.31	7.9	.338	8.6	64	11	.09	2.3	5.9	26	.16	4.2	0.041	1.0	3.00	SST	C	N
0.420	10.67	LL-95	.31	7.9	.326	8.3	117	20	.08	1.9	8.8	39	.14	3.6	0.047	1.2	3.00	SST	CG	N
0.420	10.67	MM-67	.31	7.9	.320	8.1	156	27	.06	1.6	9.9	44	.15	3.8	0.050	1.3	3.00	SST	CG	N
0.420	10.67	PP-10	.34	8.7	.340	8.6	116	20	.05	1.2	5.5	24	.14	3.6	0.040	1.0	2.50	SST	C	N
0.420	10.67	XX-51	.34	8.7	.312	7.9	108	19	.12	2.9	12	55	.22	5.5	0.054	1.4	4.00	SST	CG	N
0.420	10.67	DD-21	.38	9.5	.340	8.6	59	10	.09	2.4	5.5	24	.12	3.0	0.040	1.0	3.00	SPR	CG	Z
0.420	10.67	A9-42	.38	9.5	.334	8.5	61	11	.12	3.0	7.3	32	.15	3.8	0.043	1.1	3.50	SPR	CG	Z
0.420	10.67	S-1090	.38	9.5	.320	8.1	51	8.9	.13	3.2	6.4	28	.25	6.4	0.050	1.3	5.00	SST	CG	N
0.420	10.67	L-17	.38	9.5	.306	7.8	137	24	.09	2.3	12	55	.29	7.2	0.057	1.4	4.00	SST	C	N
0.420	10.67	M-105	.38	9.5	.296	7.5	266	47	.07	1.8	19	83	.22	5.5	0.062	1.6	3.50	SST	CG	N
0.420	10.67	II-27	.41	10.3	.382	9.7	1.3	.22	.31	7.8	.39	1.7	.10	2.5	0.019	0.5	4.25	MW	C	N
0.420	10.67	11291	.41	10.3	.338	8.6	16	2.9	.16	4.1	2.6	12	.25	6.2	0.041	1.0	6.00	SST	CG	N
0.420	10.67	10972	.41	10.3	.328	8.3	87	15	.10	2.4	8.3	37	.15	3.8	0.046	1.2	3.25	SST	CG	N
0.420	10.67	JJ-5	.41	10.3	.300	7.6	158	28	.11	2.9	18	80	.27	6.9	0.060	1.5	4.50	SPR	CG	N
0.420	10.67	10099	.41	10.3	.332	8.4	29	5.0	.17	4.2	4.7	21	.24	6.1	0.044	1.1	5.50	SPR	CG	BO
0.420	10.67	S-400	.44	11.1	.376	9.6	2.3	.40	.35	8.9	.81	3.6	.09	2.2	0.022	0.6	4.00	SST	CG	N
0.420	10.67	S-1073	.44	11.1	.370	9.4	2.0	.34	.26	6.7	.52	2.3	.18	4.4	0.025	0.6	6.00	SST	C	N
0.420	10.67	2691	.44	11.1	.338	8.6	37	6.5	.17	4.3	6.3	28	.21	5.2	0.041	1.0	4.00	SPR	C	Z
0.420	10.67	B-52	.44	11.1	.330	8.4	89	16	.10	2.5	8.3	37	.15	3.8	0.045	1.1	3.25	SPR	CG	N
0.420	10.67	YY-44	.44	11.1	.330	8.4	64	11	.12	3.1	7.8	35	.16	4.0	0.045	1.1	3.50	SST	CG	N
0.420	10.67	HH-31	.44	11.1	.326	8.3	52	9.1	.17	4.3	8.8	39	.20	5.1	0.047	1.2	4.25	SST	CG	N
0.420	10.67	3899	.44	11.1	.312	7.9	165	29	.08	2.0	13	59	.19	4.8	0.054	1.4	3.50	SPR	CG	Z
0.420	10.67	JJ-23	.44	11.1	.300	7.6	158	28	.11	2.7	17	76	.33	8.4	0.060	1.5	4.50	SPR	C	N
0.420	10.67	S-1464	.44	11.1	.276	7.0	395	69	.07	1.7	27									



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.420	10.67	3948	.50	12.7	.338	8.6	27	4.7	.23	6.0	6.3	28	.24	6.0	0.041	1.0	4.75	SPR	C	Z
0.420	10.67	71339	.50	12.7	.336	8.5	34	6.0	.28	7.0	9.4	42	.18	4.7	0.042	1.1	4.38	MW	CG	N
0.420	10.67	71339S	.50	12.7	.336	8.5	29	5.1	.22	5.6	6.4	28	.18	4.7	0.042	1.1	4.38	SST	CG	N
0.420	10.67	71351	.50	12.7	.330	8.4	43	7.6	.27	6.8	12	51	.21	5.3	0.045	1.1	4.63	MW	CG	N
0.420	10.67	71351S	.50	12.7	.330	8.4	37	6.4	.21	5.4	7.8	35	.21	5.3	0.045	1.1	4.63	SST	CG	N
0.420	10.67	71362	.50	12.7	.326	8.3	54	9.5	.24	6.1	13	58	.21	5.4	0.047	1.2	4.50	MW	CG	N
0.420	10.67	71362S	.50	12.7	.326	8.3	46	8.0	.19	4.9	8.8	39	.21	5.4	0.047	1.2	4.50	SST	CG	N
0.420	10.67	71371	.50	12.7	.324	8.2	61	11	.23	5.8	14	62	.22	5.5	0.048	1.2	4.50	MW	CG	N
0.420	10.67	71371S	.50	12.7	.324	8.2	52	9.0	.18	4.6	9.4	42	.22	5.5	0.048	1.2	4.50	SST	CG	N
0.420	10.67	71386	.50	12.7	.318	8.1	74	13	.21	5.3	16	69	.24	6.0	0.051	1.3	4.63	MW	CG	N
0.420	10.67	71386S	.50	12.7	.318	8.1	63	11	.17	4.2	11	47	.24	6.0	0.051	1.3	4.63	SST	CG	N
0.420	10.67	71397	.50	12.7	.310	7.9	95	17	.20	5.2	19	86	.27	6.8	0.055	1.4	4.88	MW	CG	N
0.420	10.67	71397S	.50	12.7	.310	7.9	81	14	.16	4.1	13	58	.27	6.8	0.055	1.4	4.88	SST	CG	N
0.420	10.67	71408	.50	12.7	.302	7.7	137	24	.17	4.4	24	106	.28	7.1	0.059	1.5	4.75	MW	CG	N
0.420	10.67	71408S	.50	12.7	.302	7.7	116	20	.14	3.5	16	72	.28	7.1	0.059	1.5	4.75	SST	CG	N
0.420	10.67	EE-97	.50	12.7	.300	7.6	158	28	.11	2.9	18	80	.27	6.9	0.060	1.5	4.50	SPR	CG	N
0.420	10.67	71419	.50	12.7	.294	7.5	183	32	.16	4.0	29	128	.30	7.6	0.063	1.6	4.75	MW	CG	N
0.420	10.67	71419S	.50	12.7	.294	7.5	155	27	.13	3.2	19	87	.30	7.6	0.063	1.6	4.75	SST	CG	N
0.420	10.67	1803	.53	13.5	.330	8.4	44	7.8	.26	6.6	12	51	.25	6.3	0.045	1.1	4.50	MW	C	Z
0.420	10.67	F-36	.53	13.5	.312	7.9	82	14	.16	4.1	13	59	.32	8.2	0.054	1.4	5.00	SPR	C	Z
0.420	10.67	71328	.56	14.2	.344	8.7	20	3.5	.35	8.9	7.0	31	.18	4.6	0.038	1.0	4.75	MW	CG	N
0.420	10.67	71328S	.56	14.2	.344	8.7	17	3.0	.28	7.1	4.7	21	.18	4.6	0.038	1.0	4.75	SST	CG	N
0.420	10.67	71340	.56	14.2	.336	8.5	31	5.4	.30	7.7	9.4	42	.19	4.9	0.042	1.1	4.63	MW	CG	N
0.420	10.67	71340S	.56	14.2	.336	8.5	26	4.6	.24	6.1	6.4	28	.19	4.9	0.042	1.1	4.63	SST	CG	N
0.420	10.67	Z-33	.56	14.3	.370	9.4	1.2	.20	.34	8.7	.40	1.8	.22	5.6	0.025	0.6	8.75	SST	CG	N
0.420	10.67	H-62	.56	14.3	.356	9.0	13	2.2	.23	5.9	3.0	13	.12	3.0	0.032	0.8	3.75	SST	CG	N
0.420	10.67	M-116	.56	14.3	.346	8.8	12	2.1	.36	9.1	4.2	19	.20	5.2	0.037	0.9	5.50	SST	CG	N
0.420	10.67	XX-60	.56	14.3	.334	8.5	23	4.0	.28	7.2	6.4	28	.28	7.1	0.043	1.1	5.50	SST	C	N
0.420	10.67	GG-57	.56	14.3	.200	5.1	3498	613	.02	.63	87	388	.44	11.2	0.110	2.8	4.00	SPR	CG	Z
0.420	10.67	11198	.59	15.1	.390	9.9	.28	.05	.50	13	.14	.61	.10	2.5	0.015	0.4	5.50	SST	C	N
0.420	10.67	3756	.59	15.1	.270	6.9	366	64	.09	2.3	32	145	.38	9.5	0.075	1.9	5.00	SPR	CG	Z
0.420	10.67	A11-52	.59	15.1	.210	5.3	2769	485	.03	.73	80	354	.42	10.7	0.105	2.7	4.00	SPR	CG	N
0.420	10.67	LL-78	.59	15.1	.210	5.3	2769	485	.03	.73	80	354	.42	10.7	0.105	2.7	4.00	SPR	CG	N
0.420	10.67	3653	.63	15.9	.364	9.2	4.9	.85	.46	12	2.2	9.9	.17	4.3	0.028	0.7	5.00	MW	C	Z
0.420	10.67	00-89	.63	15.9	.348	8.8	15	2.6	.27	7.0	4.0	18	.20	5.0	0.036	0.9	4.50	SST	C	N
0.420	10.67	S-387	.63	15.9	.336	8.5	24	4.2	.27	6.8	6.4	28	.25	6.4	0.042	1.1	5.00	SST	C	N
0.420	10.67	B11-13	.63	15.9	.336	8.5	27	4.8	.25	6.3	6.8	30	.25	6.4	0.042	1.1	5.00	SPR	C	N
0.420	10.67	B-96	.63	15.9	.332	8.4	22	3.8	.33	8.5	7.3	32	.26	6.7	0.044	1.1	6.00	SST	CG	N
0.420	10.67	3369	.63	15.9	.322	8.2	40	7.0	.27	6.7	11	47	.34	8.7	0.049	1.2	6.00	SPR	C	Z
0.420	10.67	FF-78	.63	15.9	.310	7.9	77	13	.18	4.6	14	62	.30	7.7	0.055	1.4	5.50	SPR	CG	Z
0.420	10.67	B10-30	.63	15.9	.292	7.4	134	24	.15	3.9	20	91	.35	8.9	0.064	1.6	5.50	SST	CG	N
0.420	10.67	A-95	.63	15.9	.270	6.9	212	37	.14	3.5	29	130	.49	12.4	0.075	1.9	6.50	SST	CG	N
0.420	10.67	71314	.63	16.0	.350	8.9	15	2.5	.38	9.6	5.5	24	.16	4.1	0.035	0.9	4.63	MW	CG	N
0.420	10.67	71314S	.63	16.0	.350	8.9	12	2.2	.30	7.6	3.7	16	.16	4.1	0.035	0.9	4.63	SST	CG	N
0.420	10.67	71329	.63	16.0	.344	8.7	18	3.2	.39	9.9	7.0	31	.19	4.8	0.038	1.0	5.00	MW	CG	N
0.420	10.67	71329S	.63	16.0	.344	8.7	15	2.7	.31	7.8	4.7	21	.19	4.8	0.038	1.0	5.00	SST	CG	N
0.420	10.67	71341	.63	16.0	.336	8.5	28	4.8	.34	8.7	9.4	42	.21	5.3	0.042	1.1	5.00	MW	CG	N
0.420	10.67	71341S	.63	16.0	.336	8.5	23	4.1	.27	6.9	6.4	28	.21	5.3	0.042	1.1	5.00	SST	CG	N
0.420	10.67	71352	.63	16.0	.330	8.4	34	6.0	.34	8.6	12	51	.24	6.0	0.045	1.1	5.25	MW	CG	N
0.420	10.67	71352S	.63	16.0	.330	8.4	29	5.1	.27	6.8	7.8	35	.24	6.0	0.045	1.1	5.25	SST	CG	N
0.420	10.67	71363	.63	16.0	.326	8.3	41	7.2	.32	8.1	13	58	.25	6.3	0.047	1.2	5.25	MW	CG	N
0.420	10.67	71363S	.63	16.0	.326	8.3	35	6.1	.25	6.4	8.8	39	.25	6.3	0.047	1.2	5.25	SST	CG	N
0.420	10.67	71373	.63	16.0	.324	8.2	45	7.9	.31	7.8	14	62	.25	6.4	0.048	1.2	5.25	MW	CG	N
0.420	10.67	71373S	.63	16.0	.324	8.2	38	6.7	.25	6.2	9.4	42	.25	6.4	0.048	1.2	5.25	SST	CG	N
0.420	10.67	71387	.63	16.0	.318	8.1	57	9.9	.27	7.0	16	69	.27	7.0	0.051	1.3	5.38	MW	CG	N
0.420	10.67	71387S	.63	16.0	.318	8.1	48	8.5	.22	5.5	11	47	.27	7.0	0.051	1.3	5.38	SST	CG	N
0.420	10.67	71398	.63	16.0	.310	7.9	75	13	.26	6.6	19	86	.31	7.9	0.055	1.4	5.63	MW	CG	N
0.420	10.67	71398S	.63	16.0	.310	7.9	64	11	.21	5.2	13	58	.31	7.9	0.055	1.4	5.63	SST	CG	N
0.420	10.67	71409	.63	16.0	.302	7.7	103	18	.23	5.9	24	106	.33	8.4	0.059	1.5	5.63	MW	CG	N
0.420	10.67	71409S	.63	16.0	.302	7.7	88	15	.18	4.7	16	72	.33	8.4	0.059	1.5	5.63	SST	CG	N
0.420	10.67	71420	.63	16.0	.294	7.5	137	24	.21	5.3	29	128	.35	9.0	0.063	1.6	5.63	MW	CG	N
0.420	10.67	71420S	.63	16.0	.294	7.5	117	20	.17	4.2	19	87	.35	9.0	0.063	1.6	5.63	SST	CG	N
0.420	10.67	S-798	.66	16.7	.334	8.5	20	3.5	.34	8.6	6.8	30	.26	6.6	0.043	1.1	6.00	SST	CG	N
0.420	10.67	3503	.69	17.4	.388	9.9	.57	.10	.60	15	.34	1.5	.09	2.2	0.016	0.4	4.50	MW	C	Z
0.420	10.67	B12-50	.69	17.4	.384	9.8	.37	.06	.52	13	.19	.85	.17	4.2	0.018	0.5	8.25	MW	C	N
0.420	10.67	2921	.69	17.4	.366	9.3	4.2	.73	.53	13	2.2	9.7	.16	4.1	0.027	0.7	5.00	MW	C	Z
0.420	10.67	S-1062	.69	17.4	.356	9.0	6.4	1.1	.47	12	3.0	13	.21	5.3	0.032	0.8	5.50	SST	C	N
0.420	10.67	S-3181	.69	17.4	.338	8.6	18	3.2	.32	8.2	5.9	26	.23	5.7	0.041	1.0	5.50	SST	CG	N
0.420	10.67	10187	.69	17.4	.326	8.3	34	5.9	.28	7.2	9.4	42	.33	8.4	0.04					



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.420	10.67	71330S	.75	19.1	.344	8.7	12	2.1	.39	9.9	4.7	21	.22	5.5	0.038	1.0	5.75	SST	CG	N
0.420	10.67	AA-56	.75	19.1	.344	8.7	11	1.9	.47	12	5.0	22	.27	6.8	0.038	1.0	7.00	SPR	CG	GI
0.420	10.67	B14-22	.75	19.1	.342	8.7	14	2.5	.36	9.2	5.1	23	.22	5.7	0.039	1.0	5.75	SST	CG	N
0.420	10.67	S-3007	.75	19.1	.340	8.6	17	2.9	.33	8.5	5.5	24	.26	6.6	0.040	1.0	5.50	SST	C	N
0.420	10.67	I-35	.75	19.1	.338	8.6	11	1.9	.34	8.6	3.6	16	.41	10.4	0.041	1.0	9.00	SPR	C	GI
0.420	10.67	71342	.75	19.1	.336	8.5	22	3.9	.43	11	9.4	42	.24	6.1	0.042	1.1	5.75	MW	CG	N
0.420	10.67	71342S	.75	19.1	.336	8.5	19	3.3	.34	8.6	6.4	28	.24	6.1	0.042	1.1	5.75	SST	CG	N
0.420	10.67	U-50	.75	19.1	.334	8.5	18	3.2	.40	10	7.3	32	.34	8.7	0.043	1.1	7.00	SPR	C	Z
0.420	10.67	71353	.75	19.1	.330	8.4	27	4.8	.42	11	12	51	.28	7.0	0.045	1.1	6.13	MW	CG	N
0.420	10.67	71353S	.75	19.1	.330	8.4	23	4.1	.34	8.5	7.8	35	.28	7.0	0.045	1.1	6.13	SST	CG	N
0.420	10.67	71364	.75	19.1	.326	8.3	34	6.0	.38	9.8	13	58	.28	7.2	0.047	1.2	6.00	MW	CG	N
0.420	10.67	71364S	.75	19.1	.326	8.3	29	5.1	.31	7.8	8.8	39	.28	7.2	0.047	1.2	6.00	SST	CG	N
0.420	10.67	71374	.75	19.1	.324	8.2	37	6.5	.37	9.4	14	62	.29	7.3	0.048	1.2	6.00	MW	CG	N
0.420	10.67	71374S	.75	19.1	.324	8.2	32	5.6	.30	7.5	9.4	42	.29	7.3	0.048	1.2	6.00	SST	CG	N
0.420	10.67	CC-12	.75	19.1	.320	8.1	25	4.4	.30	7.6	7.5	34	.45	11.4	0.050	1.3	9.00	HD	CG	N
0.420	10.67	71388	.75	19.1	.318	8.1	46	8.0	.34	8.7	16	69	.32	8.1	0.051	1.3	6.25	MW	CG	N
0.420	10.67	71388S	.75	19.1	.318	8.1	39	6.8	.27	6.9	11	47	.32	8.1	0.051	1.3	6.25	SST	CG	N
0.420	10.67	3816	.75	19.1	.312	7.9	55	9.6	.24	6.1	13	59	.41	10.3	0.054	1.4	6.50	SPR	CG	Z
0.420	10.67	2959	.75	19.1	.310	7.9	67	12	.21	5.3	14	62	.33	8.4	0.055	1.4	6.00	SPR	CG	Z
0.420	10.67	71399	.75	19.1	.310	7.9	62	11	.32	8.0	19	86	.35	8.9	0.055	1.4	6.38	MW	CG	N
0.420	10.67	71399S	.75	19.1	.310	7.9	52	9.2	.25	6.4	13	58	.35	8.9	0.055	1.4	6.38	SST	CG	N
0.420	10.67	71410	.75	19.1	.302	7.7	83	14	.29	7.3	24	106	.38	9.7	0.059	1.5	6.50	MW	CG	N
0.420	10.67	71410S	.75	19.1	.302	7.7	70	12	.23	5.8	16	72	.38	9.7	0.059	1.5	6.50	SST	CG	N
0.420	10.67	GG-97	.75	19.1	.296	7.5	83	15	.24	6.0	20	88	.47	11.8	0.062	1.6	7.50	HD	CG	N
0.420	10.67	S-1316	.75	19.1	.296	7.5	80	14	.23	5.9	19	83	.43	11.0	0.062	1.6	7.00	SST	CG	N
0.420	10.67	71421	.75	19.1	.294	7.5	109	19	.26	6.7	29	128	.42	10.6	0.063	1.6	6.63	MW	CG	N
0.420	10.67	71421S	.75	19.1	.294	7.5	93	16	.21	5.3	19	87	.42	10.6	0.063	1.6	6.63	SST	CG	N
0.420	10.67	71430	.75	19.1	.286	7.3	144	25	.24	6.0	34	153	.44	11.3	0.067	1.7	6.63	MW	CG	N
0.420	10.67	71430S	.75	19.1	.286	7.3	123	21	.19	4.8	23	104	.44	11.3	0.067	1.7	6.63	SST	CG	N
0.420	10.67	2876	.75	19.1	.284	7.2	140	24	.18	4.7	26	115	.48	12.1	0.068	1.7	7.00	SPR	CG	GI
0.420	10.67	00-40	.75	19.1	.260	6.6	263	46	.14	3.5	37	163	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.420	10.67	L-63	.78	19.8	.380	9.7	.89	.16	.64	16	.57	2.5	.14	3.6	0.020	0.5	6.00	MW	C	Z
0.420	10.67	HH-61	.81	20.6	.376	9.6	.92	.16	.64	16	.59	2.6	.18	4.5	0.022	0.6	7.00	SST	C	N
0.420	10.67	L-12	.81	20.6	.352	8.9	4.8	.84	.54	14	2.6	12	.27	6.9	0.034	0.9	8.00	SST	CG	N
0.420	10.67	A9-54	.81	20.6	.352	8.9	3.7	.64	.47	12	1.7	7.7	.34	8.6	0.034	0.9	10.0	SST	CG	N
0.420	10.67	10553	.81	20.6	.300	7.6	88	15	.20	5.2	18	80	.39	9.9	0.060	1.5	6.50	SPR	CG	Z
0.420	10.67	S-1205	.81	20.6	.276	7.0	144	25	.19	4.8	27	120	.54	13.7	0.072	1.8	7.50	SST	CG	N
0.420	10.67	10521	.84	21.4	.338	8.6	11	1.9	.52	13	5.6	25	.33	8.3	0.041	1.0	8.00	SST	CG	N
0.420	10.67	1679	.84	21.4	.338	8.6	12	2.2	.47	12	5.8	26	.37	9.4	0.041	1.0	8.00	SPR	C	Z
0.420	10.67	10880	.84	21.4	.286	7.3	97	17	.24	6.1	23	104	.54	13.6	0.067	1.7	8.00	SST	CG	N
0.420	10.67	B2-42	.84	21.4	.312	7.9	59	10	.23	5.7	13	59	.34	8.6	0.054	1.4	6.25	SPR	CG	GI
0.420	10.67	S-1542	.88	22.2	.338	8.6	6.4	1.1	.38	9.7	2.5	11	.49	12.5	0.041	1.0	12.0	SST	CG	N
0.420	10.67	3593	.88	22.2	.312	7.9	45	7.9	.41	10	18	82	.46	11.7	0.054	1.4	7.50	MW	C	Z
0.420	10.67	10298	.88	22.2	.310	7.9	54	9.4	.26	6.6	14	62	.39	9.8	0.055	1.4	7.00	SPR	CG	Z
0.420	10.67	S-1050	.88	22.2	.296	7.5	73	13	.26	6.5	19	83	.47	11.8	0.062	1.6	7.50	SST	CG	N
0.420	10.67	12506	.88	22.2	.296	7.5	115	20	.16	4.1	19	83	.34	8.7	0.062	1.6	5.50	SST	CG	N
0.420	10.67	Q-76	.88	22.2	.278	7.1	126	22	.21	5.2	26	116	.57	14.4	0.071	1.8	8.00	SST	CG	N
0.420	10.67	Z-96	.88	22.2	.276	7.0	122	21	.22	5.7	27	120	.61	15.5	0.072	1.8	8.50	SST	CG	N
0.420	10.67	S-1052	.88	22.2	.260	6.6	235	41	.16	4.0	37	163	.60	15.2	0.080	2.0	7.50	SST	CG	N
0.420	10.67	S-482	.88	22.2	.260	6.6	215	38	.17	4.3	37	163	.64	16.3	0.080	2.0	8.00	SST	CG	N
0.420	10.67	71316	.88	22.4	.350	8.9	10	1.8	.55	14	5.5	24	.20	5.1	0.035	0.9	5.75	MW	CG	N
0.420	10.67	71316S	.88	22.4	.350	8.9	8.5	1.5	.44	11	3.7	16	.20	5.1	0.035	0.9	5.75	SST	CG	N
0.420	10.67	71331	.88	22.4	.344	8.7	12	2.1	.57	14	7.0	31	.24	6.2	0.038	1.0	6.38	MW	CG	N
0.420	10.67	71331S	.88	22.4	.344	8.7	10	1.8	.45	12	4.7	21	.24	6.2	0.038	1.0	6.38	SST	CG	N
0.420	10.67	71343	.88	22.4	.336	8.5	19	3.2	.51	13	9.4	42	.27	6.9	0.042	1.1	6.50	MW	CG	N
0.420	10.67	71343S	.88	22.4	.336	8.5	16	2.8	.40	10	6.4	28	.27	6.9	0.042	1.1	6.50	SST	CG	N
0.420	10.67	71354	.88	22.4	.330	8.4	23	4.0	.50	13	12	51	.31	7.9	0.045	1.1	6.88	MW	CG	N
0.420	10.67	71354S	.88	22.4	.330	8.4	20	3.4	.40	10	7.8	35	.31	7.9	0.045	1.1	6.88	SST	CG	N
0.420	10.67	71365	.88	22.4	.326	8.3	28	4.9	.47	12	13	58	.32	8.2	0.047	1.2	6.88	MW	CG	N
0.420	10.67	71365S	.88	22.4	.326	8.3	24	4.2	.37	9.4	8.8	39	.32	8.2	0.047	1.2	6.88	SST	CG	N
0.420	10.67	71376	.88	22.4	.324	8.2	31	5.4	.45	12	14	62	.33	8.4	0.048	1.2	6.88	MW	CG	N
0.420	10.67	71376S	.88	22.4	.324	8.2	26	4.6	.36	9.2	9.4	42	.33	8.4	0.048	1.2	6.88	SST	CG	N
0.420	10.67	71389	.88	22.4	.318	8.1	38	6.7	.41	10	16	69	.36	9.2	0.051	1.3	7.13	MW	CG	N
0.420	10.67	71389S	.88	22.4	.318	8.1	32	5.7	.33	8.3	11	47	.36	9.2	0.051	1.3	7.13	SST	CG	N
0.420	10.67	71400	.88	22.4	.310	7.9	52	9.1	.37	9.5	19	86	.40	10.1	0.055	1.4	7.25	MW	CG	N
0.420	10.67	71400S	.88	22.4	.310	7.9	44	7.7	.30	7.5	13	58	.40	10.1	0.055	1.4	7.25	SST	CG	N
0.420	10.67	71411	.88	22.4	.302	7.7	69	12	.35	8.8	24	106	.44	11.1	0.059	1.5	7.38	MW	CG	N
0.420	10.67	71411S	.88	22.4	.302	7.7	58	10	.28	7.0	16	72	.44	11.1	0.059	1.5	7.38	SST	CG	N
0.420	10.67	7142																		



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.420	10.67	71317	1.00	25.4	.350	8.9	8.7	1.5	.63	16	5.5	24	.22	5.7	0.035	0.9	6.38	MW	CG	N
0.420	10.67	71317S	1.00	25.4	.350	8.9	7.4	1.3	.50	13	3.7	16	.22	5.7	0.035	0.9	6.38	SST	CG	N
0.420	10.67	71332	1.00	25.4	.344	8.7	11	1.9	.64	16	7.0	31	.26	6.6	0.038	1.0	6.88	MW	CG	N
0.420	10.67	71332S	1.00	25.4	.344	8.7	9.4	1.6	.51	13	4.7	21	.26	6.6	0.038	1.0	6.88	SST	CG	N
0.420	10.67	I-40	1.00	25.4	.340	8.6	8.3	1.5	.60	15	5.0	22	.40	10.2	0.040	1.0	10.0	SPR	CG	N
0.420	10.67	I-29	1.00	25.4	.336	8.5	10	1.8	.58	15	6.0	26	.42	10.7	0.042	1.1	10.0	SPR	CG	BO
0.420	10.67	71344	1.00	25.4	.336	8.5	16	2.8	.59	15	9.4	42	.30	7.6	0.042	1.1	7.13	MW	CG	N
0.420	10.67	71344S	1.00	25.4	.336	8.5	14	2.4	.47	12	6.4	28	.30	7.6	0.042	1.1	7.13	SST	CG	N
0.420	10.67	10404	1.00	25.4	.330	8.4	20	3.5	.41	10	8.3	37	.34	8.6	0.045	1.1	7.50	SPR	CG	Z
0.420	10.67	71355	1.00	25.4	.330	8.4	20	3.5	.58	15	12	51	.34	8.7	0.045	1.1	7.63	MW	CG	N
0.420	10.67	71355S	1.00	25.4	.330	8.4	17	3.0	.46	12	7.8	35	.34	8.7	0.045	1.1	7.63	SST	CG	N
0.420	10.67	71366	1.00	25.4	.326	8.3	25	4.4	.52	13	13	58	.35	8.8	0.047	1.2	7.38	MW	CG	N
0.420	10.67	71366S	1.00	25.4	.326	8.3	21	3.7	.42	11	8.8	39	.35	8.8	0.047	1.2	7.38	SST	CG	N
0.420	10.67	71377	1.00	25.4	.324	8.2	27	4.7	.51	13	14	62	.36	9.1	0.048	1.2	7.50	MW	CG	N
0.420	10.67	71377S	1.00	25.4	.324	8.2	23	4.0	.41	10	9.4	42	.36	9.1	0.048	1.2	7.50	SST	CG	N
0.420	10.67	Z-18	1.00	25.4	.322	8.2	23	4.0	.46	12	11	47	.44	11.2	0.049	1.2	9.00	SPR	CG	Z
0.420	10.67	71390	1.00	25.4	.318	8.1	33	5.8	.47	12	16	69	.40	10.2	0.051	1.3	7.88	MW	CG	N
0.420	10.67	71390S	1.00	25.4	.318	8.1	28	4.9	.38	9.6	11	47	.40	10.2	0.051	1.3	7.88	SST	CG	N
0.420	10.67	71401	1.00	25.4	.310	7.9	45	7.8	.44	11	19	86	.45	11.4	0.055	1.4	8.13	MW	CG	N
0.420	10.67	71401S	1.00	25.4	.310	7.9	38	6.6	.35	8.8	13	58	.45	11.4	0.055	1.4	8.13	SST	CG	N
0.420	10.67	71412	1.00	25.4	.302	7.7	59	10	.40	10	24	106	.49	12.4	0.059	1.5	8.25	MW	CG	N
0.420	10.67	71412S	1.00	25.4	.302	7.7	50	8.8	.32	8.1	16	72	.49	12.4	0.059	1.5	8.25	SST	CG	N
0.420	10.67	71423	1.00	25.4	.294	7.5	78	14	.37	9.4	29	128	.53	13.4	0.063	1.6	8.38	MW	CG	N
0.420	10.67	71423S	1.00	25.4	.294	7.5	66	12	.29	7.5	19	87	.53	13.4	0.063	1.6	8.38	SST	CG	N
0.420	10.67	71431	1.00	25.4	.286	7.3	103	18	.33	8.5	34	153	.56	14.3	0.067	1.7	8.38	MW	CG	N
0.420	10.67	71431S	1.00	25.4	.286	7.3	87	15	.27	6.8	23	104	.56	14.3	0.067	1.7	8.38	SST	CG	N
0.420	10.67	S-177	1.00	25.4	.276	7.0	113	20	.24	6.1	27	120	.65	16.5	0.072	1.8	9.00	SST	CG	N
0.420	10.67	71438	1.00	25.4	.276	7.0	139	24	.29	7.4	40	180	.62	15.8	0.072	1.8	8.63	MW	CG	N
0.420	10.67	71438S	1.00	25.4	.276	7.0	118	21	.23	5.8	27	120	.62	15.8	0.072	1.8	8.63	SST	CG	N
0.420	10.67	10729	1.03	26.2	.360	9.1	4.3	.76	.84	21	3.6	16	.20	5.0	0.030	0.8	6.50	MW	CG	Z
0.420	10.67	MM-36	1.03	26.2	.340	8.6	13	2.3	.44	11	5.9	26	.32	8.1	0.040	1.0	7.00	SPR	C	Z
0.420	10.67	3650	1.03	26.2	.310	7.9	45	7.8	.31	7.9	14	62	.50	12.6	0.055	1.4	8.00	SPR	C	Z
0.420	10.67	B9-2	1.06	27.0	.332	8.4	18	3.2	.43	11	7.8	35	.33	8.4	0.044	1.1	7.50	SPR	CG	Z
0.420	10.67	2543	1.13	28.6	.356	9.0	3.2	.56	.77	20	2.5	11	.35	8.9	0.032	0.8	10.0	SPR	C	Z
0.420	10.67	S-52	1.13	28.6	.310	7.9	25	4.3	.44	11	11	48	.69	17.5	0.055	1.4	11.5	SST	C	N
0.420	10.67	B3-47	1.19	30.1	.304	7.7	37	6.5	.41	10	15	68	.58	14.7	0.058	1.5	10.0	SST	CG	N
0.420	10.67	CC-98	1.19	30.2	.370	9.4	1.5	.26	.95	24	1.4	6.3	.21	5.2	0.025	0.6	7.25	SST	C	N
0.420	10.67	3937	1.19	30.2	.276	7.0	91	16	.32	8.1	29	129	.86	21.9	0.072	1.8	12.0	SPR	CG	Z
0.420	10.67	10477	1.22	31.0	.310	7.9	35	6.1	.40	10	14	62	.54	13.6	0.055	1.4	9.75	SPR	CG	Z
0.420	10.67	B-99	1.25	31.8	.382	9.7	.37	.07	1.0	27	.39	1.7	.20	5.2	0.019	0.5	9.75	MW	C	N
0.420	10.67	10589	1.25	31.8	.378	9.6	.26	.05	.87	22	.22	1.0	.38	9.6	0.021	0.5	17.0	SST	C	N
0.420	10.67	10094	1.25	31.8	.352	8.9	3.7	.64	.84	21	3.1	14	.41	10.4	0.034	0.9	11.0	SPR	C	Z
0.420	10.67	71318	1.25	31.8	.350	8.9	6.9	1.2	.80	20	5.5	24	.26	6.7	0.035	0.9	7.50	MW	CG	N
0.420	10.67	71318S	1.25	31.8	.350	8.9	5.8	1.0	.64	16	3.7	16	.26	6.7	0.035	0.9	7.50	SST	CG	N
0.420	10.67	3617	1.25	31.8	.348	8.8	5.6	.99	.76	19	4.3	19	.34	8.7	0.036	0.9	9.50	HD	CG	Z
0.420	10.67	10596	1.25	31.8	.346	8.8	6.3	1.1	.74	19	4.7	21	.35	8.9	0.037	0.9	9.50	SPR	CG	Z
0.420	10.67	71333	1.25	31.8	.344	8.7	8.5	1.5	.82	21	7.0	31	.32	8.1	0.038	1.0	8.38	MW	CG	N
0.420	10.67	71333S	1.25	31.8	.344	8.7	7.2	1.3	.65	17	4.7	21	.32	8.1	0.038	1.0	8.38	SST	CG	N
0.420	10.67	71345	1.25	31.8	.336	8.5	13	2.3	.72	18	9.4	42	.35	8.9	0.042	1.1	8.38	MW	CG	N
0.420	10.67	71345S	1.25	31.8	.336	8.5	11	1.9	.57	15	6.4	28	.35	8.9	0.042	1.1	8.38	SST	CG	N
0.420	10.67	71356	1.25	31.8	.330	8.4	16	2.8	.73	18	12	51	.41	10.3	0.045	1.1	9.00	MW	CG	N
0.420	10.67	71356S	1.25	31.8	.330	8.4	13	2.4	.58	15	7.8	35	.41	10.3	0.045	1.1	9.00	SST	CG	N
0.420	10.67	71367	1.25	31.8	.326	8.3	19	3.3	.69	17	13	58	.43	10.9	0.047	1.2	9.13	MW	CG	N
0.420	10.67	71367S	1.25	31.8	.326	8.3	16	2.8	.55	14	8.8	39	.43	10.9	0.047	1.2	9.13	SST	CG	N
0.420	10.67	71378	1.25	31.8	.324	8.2	21	3.7	.66	17	14	62	.43	11.0	0.048	1.2	9.00	MW	CG	N
0.420	10.67	71378S	1.25	31.8	.324	8.2	18	3.2	.52	13	9.4	42	.43	11.0	0.048	1.2	9.00	SST	CG	N
0.420	10.67	71391	1.25	31.8	.318	8.1	26	4.5	.60	15	16	69	.48	12.3	0.051	1.3	9.50	MW	CG	N
0.420	10.67	71391S	1.25																	



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.420	10.67	S-1489	1.44	36.5	.312	7.9	30	5.2	.42	11	12	55	.50	12.7	0.054	1.4	9.25	SST	CG	N
0.420	10.67	A13-30	1.44	36.5	.198	5.0	862	151	.10	2.6	89	398	1.17	29.6	0.111	2.8	10.5	SPR	CG	N
0.420	10.67	S-402	1.47	37.3	.258	6.6	161	28	.24	6.0	38	168	.85	21.6	0.081	2.1	10.5	SST	CG	N
0.420	10.67	S-1204	1.50	38.1	.380	9.7		.22 .04	1.2	29		.26 1.1	.34	8.6	0.020	0.5	16.0	SST	C	N
0.420	10.67	RR-40	1.50	38.1	.368	9.3		.89 .16	1.1	28		.99 4.4	.39	9.9	0.026	0.7	14.0	MW	C	Z
0.420	10.67	11305	1.50	38.1	.364	9.2		1.7 .30	1.2	30		2.0 9.0	.32	8.2	0.028	0.7	10.5	MW	C	GI
0.420	10.67	71319	1.50	38.1	.350	8.9		5.6 .98	.98	25		5.5 24	.31	7.8	0.035	0.9	8.75	MW	CG	N
0.420	10.67	71319S	1.50	38.1	.350	8.9		4.8 .83	.78	20		3.7 16	.31	7.8	0.035	0.9	8.75	SST	CG	N
0.420	10.67	10230	1.50	38.1	.344	8.7		7.4 1.3	.69	17		5.0 22	.39	9.9	0.038	1.0	9.25	SPR	C	Z
0.420	10.67	71334	1.50	38.1	.344	8.7		7.1 1.2	.98	25		7.0 31	.37	9.3	0.038	1.0	9.63	MW	CG	N
0.420	10.67	71334S	1.50	38.1	.344	8.7		6.0 1.1	.78	20		4.7 21	.37	9.3	0.038	1.0	9.63	SST	CG	N
0.420	10.67	71346	1.50	38.1	.336	8.5	11	1.8	.89	23		9.4 42	.41	10.5	0.042	1.1	9.88	MW	CG	N
0.420	10.67	71346S	1.50	38.1	.336	8.5		8.9 1.6	.71	18		6.4 28	.41	10.5	0.042	1.1	9.88	SST	CG	N
0.420	10.67	71357	1.50	38.1	.330	8.4	13	2.3	.89	23		12 51	.48	12.1	0.045	1.1	10.6	MW	CG	N
0.420	10.67	71357S	1.50	38.1	.330	8.4	11	1.9	.71	18		7.8 35	.48	12.1	0.045	1.1	10.6	SST	CG	N
0.420	10.67	S-3137	1.50	38.1	.326	8.3	16	2.7	.57	14		8.8 39	.45	11.3	0.047	1.2	9.50	SST	CG	N
0.420	10.67	71368	1.50	38.1	.326	8.3	16	2.7	.84	21		13 58	.51	12.8	0.047	1.2	10.8	MW	CG	N
0.420	10.67	71368S	1.50	38.1	.326	8.3	13	2.3	.67	17		8.8 39	.51	12.8	0.047	1.2	10.8	SST	CG	N
0.420	10.67	71379	1.50	38.1	.324	8.2	17	3.0	.81	21		14 62	.51	13.0	0.048	1.2	10.6	MW	CG	N
0.420	10.67	71379S	1.50	38.1	.324	8.2	15	2.6	.64	16		9.4 42	.51	13.0	0.048	1.2	10.6	SST	CG	N
0.420	10.67	71392	1.50	38.1	.318	8.1	21	3.7	.74	19		16 69	.57	14.4	0.051	1.3	11.1	MW	CG	N
0.420	10.67	71392S	1.50	38.1	.318	8.1	18	3.1	.59	15		11 47	.57	14.4	0.051	1.3	11.1	SST	CG	N
0.420	10.67	A16-68	1.50	38.1	.318	8.1	13	2.2	.62	16		7.9 35	.88	22.4	0.051	1.3	17.3	MW	CG	N
0.420	10.67	YY-69	1.50	38.1	.312	7.9	26	4.6	.51	13		13 59	.68	17.1	0.054	1.4	11.5	SPR	C	Z
0.420	10.67	71403	1.50	38.1	.310	7.9	29	5.0	.68	17		19 86	.63	16.1	0.055	1.4	11.5	MW	CG	N
0.420	10.67	71403S	1.50	38.1	.310	7.9	24	4.2	.54	14		13 58	.63	16.1	0.055	1.4	11.5	SST	CG	N
0.420	10.67	71414	1.50	38.1	.302	7.7	38	6.6	.63	16		24 106	.69	17.6	0.059	1.5	11.8	MW	CG	N
0.420	10.67	71414S	1.50	38.1	.302	7.7	32	5.6	.50	13		16 72	.69	17.6	0.059	1.5	11.8	SST	CG	N
0.420	10.67	CC-82	1.50	38.1	.300	7.6	32	5.6	.53	13		17 75	.78	19.8	0.060	1.5	13.0	SST	CG	N
0.420	10.67	S-1395	1.50	38.1	.296	7.5	44	7.8	.42	11		19 83	.68	17.3	0.062	1.6	11.0	SST	CG	N
0.420	10.67	71425	1.50	38.1	.294	7.5	50	8.7	.58	15		29 128	.76	19.2	0.063	1.6	12.0	MW	CG	N
0.420	10.67	71425S	1.50	38.1	.294	7.5	42	7.4	.46	12		19 87	.76	19.2	0.063	1.6	12.0	SST	CG	N
0.420	10.67	71433	1.50	38.1	.286	7.3	65	11	.53	13		34 153	.81	20.6	0.067	1.7	12.1	MW	CG	N
0.420	10.67	71433S	1.50	38.1	.286	7.3	55	9.7	.42	11		23 104	.81	20.6	0.067	1.7	12.1	SST	CG	N
0.420	10.67	71440	1.50	38.1	.276	7.0	88	15	.46	12		40 180	.89	22.6	0.072	1.8	12.4	MW	CG	N
0.420	10.67	71440S	1.50	38.1	.276	7.0	75	13	.36	9.2		27 120	.89	22.6	0.072	1.8	12.4	SST	CG	N
0.420	10.67	S-841	1.56	39.7	.338	8.6		7.3 1.3	.82	21		5.9 26	.45	11.3	0.041	1.0	11.0	SST	CG	N
0.420	10.67	I-56	1.63	41.3	.292	7.4	44	7.7	.49	12		22 96	.90	22.8	0.064	1.6	14.0	SPR	CG	Z
0.420	10.67	11239	1.63	41.3	.256	6.5	148	26	.26	6.7		39 174	.98	25.0	0.082	2.1	12.0	SST	CG	N
0.420	10.67	71320	1.75	44.5	.350	8.9		4.9 .85	1.1	29		5.5 24	.34	8.7	0.035	0.9	9.75	MW	CG	N
0.420	10.67	71320S	1.75	44.5	.350	8.9		4.1 .72	.90	23		3.7 16	.34	8.7	0.035	0.9	9.75	SST	CG	N
0.420	10.67	12110	1.75	44.5	.350	8.9		4.2 .73	.95	24		4.0 18	.42	10.7	0.035	0.9	11.0	SPR	C	Z
0.420	10.67	71335	1.75	44.5	.344	8.7		6.3 1.1	1.1	28		7.0 31	.40	10.1	0.038	1.0	10.5	MW	CG	N
0.420	10.67	71335S	1.75	44.5	.344	8.7		5.4 .94	.88	22		4.7 21	.40	10.1	0.038	1.0	10.5	SST	CG	N
0.420	10.67	71347	1.75	44.5	.336	8.5		9.2 1.6	1.0	26		9.4 42	.46	11.7	0.042	1.1	11.0	MW	CG	N
0.420	10.67	71347S	1.75	44.5	.336	8.5		7.8 1.4	.82	21		6.4 28	.46	11.7	0.042	1.1	11.0	SST	CG	N
0.420	10.67	71358	1.75	44.5	.330	8.4	11	2.0	1.0	26		12 51	.53	13.4	0.045	1.1	11.8	MW	CG	N
0.420	10.67	71358S	1.75	44.5	.330	8.4		9.7 1.7	.80	20		7.8 35	.53	13.4	0.045	1.1	11.8	SST	CG	N
0.420	10.67	71369	1.75	44.5	.326	8.3	14	2.4	.97	25		13 58	.56	14.3	0.047	1.2	12.0	MW	CG	N
0.420	10.67	71369S	1.75	44.5	.326	8.3	11	2.0	.77	20		8.8 39	.56	14.3	0.047	1.2	12.0	SST	CG	N
0.420	10.67	71380	1.75	44.5	.324	8.2	15	2.6	.94	24		14 62	.58	14.6	0.048	1.2	12.0	MW	CG	N
0.420	10.67	71380S	1.75	44.5	.324	8.2	13	2.2	.75	19		9.4 42	.58	14.6	0.048	1.2	12.0	SST	CG	N
0.420	10.67	3432	1.75	44.5	.320	8.1	23	4.0	.47	12		11 47	.49	12.4	0.050	1.3	9.75	SPR	CG	Z
0.420	10.67	71393	1.75	44.5	.318	8.1	17	3.0	.89	23		16 69	.67	17.0	0.051	1.3	13.1	MW	CG	N
0.420	10.67	71393S	1.75	44.5	.318	8.1	15	2.6	.71	18		11 47	.67	17.0	0.051	1.3	13.1	SST	CG	N
0.420	10.67	71404	1.75	44.5	.310	7.9	24	4.2	.80	20		19 86	.72	18.3	0.055	1.4	13.1	MW	CG	N
0.420	10.67	71404S	1.75	44.5	.310	7.9	21	3.6	.64	16		13 58	.72	18.3	0.055	1.4	13.1	SST	CG	N
0.420	10.67	71415	1.75	44.5	.302	7.7	32	5.6	.74	19		24 106	.80	20.4	0.059	1.5	13.6	MW	CG	N



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.420	10.67	71370S	2.00	50.8	.326	8.3	9.8	1.7	.90	23	8.8	39	.65	16.4	0.047	1.2	13.8	SST	CG	N
0.420	10.67	71381	2.00	50.8	.324	8.2	13	2.3	1.1	27	14	62	.65	16.5	0.048	1.2	13.5	MW	CG	N
0.420	10.67	71381S	2.00	50.8	.324	8.2	11	1.9	.86	22	9.4	42	.65	16.5	0.048	1.2	13.5	SST	CG	N
0.420	10.67	71394	2.00	50.8	.318	8.1	16	2.7	1.0	25	16	69	.74	18.8	0.051	1.3	14.5	MW	CG	N
0.420	10.67	71394S	2.00	50.8	.318	8.1	13	2.3	.80	20	11	47	.74	18.8	0.051	1.3	14.5	SST	CG	N
0.420	10.67	71405	2.00	50.8	.310	7.9	21	3.7	.92	23	19	86	.81	20.6	0.055	1.4	14.8	MW	CG	N
0.420	10.67	71405S	2.00	50.8	.310	7.9	18	3.1	.73	19	13	58	.81	20.6	0.055	1.4	14.8	SST	CG	N
0.420	10.67	71416	2.00	50.8	.302	7.7	28	4.9	.86	22	24	106	.91	23.0	0.059	1.5	15.4	MW	CG	N
0.420	10.67	71416S	2.00	50.8	.302	7.7	24	4.1	.68	17	16	72	.91	23.0	0.059	1.5	15.4	SST	CG	N
0.420	10.67	71427	2.00	50.8	.294	7.5	36	6.4	.79	20	29	128	.99	25.2	0.063	1.6	15.8	MW	CG	N
0.420	10.67	71427S	2.00	50.8	.294	7.5	31	5.4	.63	16	19	87	.99	25.2	0.063	1.6	15.8	SST	CG	N
0.420	10.67	71435	2.00	50.8	.286	7.3	48	8.3	.72	18	34	153	1.06	27.0	0.067	1.7	15.9	MW	CG	N
0.420	10.67	71435S	2.00	50.8	.286	7.3	40	7.1	.58	15	23	104	1.06	27.0	0.067	1.7	15.9	SST	CG	N
0.420	10.67	71442	2.00	50.8	.276	7.0	64	11	.63	16	40	180	1.17	29.7	0.072	1.8	16.3	MW	CG	N
0.420	10.67	71442S	2.00	50.8	.276	7.0	55	9.6	.50	13	27	120	1.17	29.7	0.072	1.8	16.3	SST	CG	N
0.420	10.67	4374	2.06	52.4	.276	7.0	62	11	.47	12	29	129	1.21	30.6	0.072	1.8	16.8	SPR	CG	Z
0.420	10.67	71324	2.25	57.2	.350	8.9	3.8	.67	1.4	37	5.5	24	.42	10.7	0.035	0.9	12.0	MW	CG	N
0.420	10.67	71324S	2.25	57.2	.350	8.9	3.2	.57	1.1	29	3.7	16	.42	10.7	0.035	0.9	12.0	SST	CG	N
0.420	10.67	S-1410	2.25	57.2	.346	8.8	5.2	.91	.85	21	4.4	19	.41	10.3	0.037	0.9	10.0	SST	C	N
0.420	10.67	71337	2.25	57.2	.344	8.7	5.0	.88	1.4	36	7.0	31	.48	12.3	0.038	1.0	12.8	MW	CG	N
0.420	10.67	71337S	2.25	57.2	.344	8.7	4.3	.74	1.1	28	4.7	21	.48	12.3	0.038	1.0	12.8	SST	CG	N
0.420	10.67	71349	2.25	57.2	.336	8.5	7.2	1.3	1.3	33	9.4	42	.57	14.4	0.042	1.1	13.5	MW	CG	N
0.420	10.67	71349S	2.25	57.2	.336	8.5	6.1	1.1	1.0	26	6.4	28	.57	14.4	0.042	1.1	13.5	SST	CG	N
0.420	10.67	71360	2.25	57.2	.330	8.4	8.7	1.5	1.3	34	12	51	.67	17.0	0.045	1.1	14.9	MW	CG	N
0.420	10.67	71360S	2.25	57.2	.330	8.4	7.4	1.3	1.1	27	7.8	35	.67	17.0	0.045	1.1	14.9	SST	CG	N
0.420	10.67	71383	2.25	57.2	.324	8.2	11	1.9	1.3	32	14	62	.74	18.7	0.048	1.2	15.4	MW	CG	N
0.420	10.67	71383S	2.25	57.2	.324	8.2	9.4	1.7	1.0	25	9.4	42	.74	18.7	0.048	1.2	15.4	SST	CG	N
0.420	10.67	71395	2.25	57.2	.318	8.1	14	2.4	1.1	29	16	69	.82	20.7	0.051	1.3	16.0	MW	CG	N
0.420	10.67	71395S	2.25	57.2	.318	8.1	12	2.1	.90	23	11	47	.82	20.7	0.051	1.3	16.0	SST	CG	N
0.420	10.67	71406	2.25	57.2	.310	7.9	18	3.2	1.1	27	19	86	.92	23.4	0.055	1.4	16.8	MW	CG	N
0.420	10.67	71406S	2.25	57.2	.310	7.9	16	2.7	.84	21	13	58	.92	23.4	0.055	1.4	16.8	SST	CG	N
0.420	10.67	71417	2.25	57.2	.302	7.7	25	4.3	.97	25	24	106	1.01	25.7	0.059	1.5	17.1	MW	CG	N
0.420	10.67	71417S	2.25	57.2	.302	7.7	21	3.6	.77	20	16	72	1.01	25.7	0.059	1.5	17.1	SST	CG	N
0.420	10.67	71428	2.25	57.2	.294	7.5	32	5.6	.90	23	29	128	1.10	28.0	0.063	1.6	17.5	MW	CG	N
0.420	10.67	71428S	2.25	57.2	.294	7.5	27	4.8	.72	18	19	87	1.10	28.0	0.063	1.6	17.5	SST	CG	N
0.420	10.67	71436	2.25	57.2	.286	7.3	42	7.4	.82	21	34	153	1.18	30.0	0.067	1.7	17.6	MW	CG	N
0.420	10.67	71436S	2.25	57.2	.286	7.3	36	6.3	.65	17	23	104	1.18	30.0	0.067	1.7	17.6	SST	CG	N
0.420	10.67	71443	2.25	57.2	.276	7.0	57	9.9	.71	18	40	180	1.31	33.4	0.072	1.8	18.3	MW	CG	N
0.420	10.67	71443S	2.25	57.2	.276	7.0	48	8.4	.56	14	27	120	1.31	33.4	0.072	1.8	18.3	SST	CG	N
0.420	10.67	4243	2.38	60.3	.360	9.1	1.5	.26	1.9	48	2.8	13	.48	12.2	0.030	0.8	15.0	MW	C	Z
0.420	10.67	10568	2.38	60.3	.268	6.8	62	11	.55	14	34	150	1.59	40.4	0.076	1.9	210.0	SPR	CG	N
0.420	10.67	10615	2.50	63.5	.370	9.4	.62	.11	2.1	53	1.3	5.8	.40	10.2	0.025	0.6	15.0	SST	C	N
0.420	10.67	71326	2.50	63.5	.350	8.9	3.4	.60	1.6	41	5.5	24	.46	11.7	0.035	0.9	13.1	MW	CG	N
0.420	10.67	71326S	2.50	63.5	.350	8.9	2.9	.51	1.3	33	3.7	16	.46	11.7	0.035	0.9	13.1	SST	CG	N
0.420	10.67	71338	2.50	63.5	.344	8.7	4.5	.79	1.6	39	7.0	31	.53	13.5	0.038	1.0	14.0	MW	CG	N
0.420	10.67	71338S	2.50	63.5	.344	8.7	3.8	.67	1.2	31	4.7	21	.53	13.5	0.038	1.0	14.0	SST	CG	N
0.420	10.67	71350	2.50	63.5	.336	8.5	6.5	1.1	1.5	37	9.4	42	.62	15.9	0.042	1.1	14.9	MW	CG	N
0.420	10.67	71350S	2.50	63.5	.336	8.5	5.5	.96	1.2	29	6.4	28	.62	15.9	0.042	1.1	14.9	SST	CG	N
0.420	10.67	71361	2.50	63.5	.330	8.4	7.9	1.4	1.5	37	12	51	.73	18.6	0.045	1.1	16.3	MW	CG	N
0.420	10.67	71361S	2.50	63.5	.330	8.4	6.7	1.2	1.2	30	7.8	35	.73	18.6	0.045	1.1	16.3	SST	CG	N
0.420	10.67	71385	2.50	63.5	.324	8.2	9.9	1.7	1.4	36	14	62	.82	20.7	0.048	1.2	17.0	MW	CG	N
0.420	10.67	71385S	2.50	63.5	.324	8.2	8.4	1.5	1.1	28	9.4	42	.82	20.7	0.048	1.2	17.0	SST	CG	N
0.420	10.67	71396	2.50	63.5	.318	8.1	12	2.2	1.3	32	16	69	.90	22.8	0.051	1.3	17.6	MW	CG	N
0.420	10.67	71396S	2.50	63.5	.318	8.1	10	1.8	1.0	25	11	47	.90	22.8	0.051	1.3	17.6	SST	CG	N
0.420	10.67	71407	2.50	63.5	.310	7.9	17	2.9	1.2	30	19	86	1.01	25.7	0.055	1.4	18.4	MW	CG	N
0.420	10.67	71407S	2.50	63.5	.310	7.9	14	2.5	.94	24	13	58	1.01	25.7	0.055	1.4	18.4	SST	CG	N
0.420	10.67	71418	2.50	63.5	.302	7.7	22	3.8	1.1	28	24	106	1							




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.420	10.67	11666	9.50	241.3	.322	8.2	2.0	.34	5.4	137	11	47	4.12	104.5	0.049	1.2	84.0	SPR	CG	GI
0.420	10.67	S-424	15.8	400.1	.346	8.8	.32	.06	11	274	3.4	15	4.96	125.9	0.037	0.9	133.0	SST	C	N
0.432	10.97	B3-63	1.23	31.3	.280	7.1	132	23	.23	5.9	31	137	.68	17.4	0.076	1.9	9.00	SST	CG	N
0.437	11.10	S-1266	.31	7.9	.407	10.3	.21	.04	.21	5.3	.04	.19	.11	2.7	0.015	0.4	6.00	SST	C	N
0.437	11.10	12611	.31	7.9	.391	9.9	.99	.17	.13	3.3	.13	.56	.18	4.7	0.023	0.6	7.00	SST	C	N
0.437	11.10	11454	.31	7.9	.387	9.8	3.6	.62	.19	4.7	.67	3.0	.13	3.2	0.025	0.6	4.00	SST	C	N
0.437	11.10	A15-44	.34	8.7	.355	9.0	26	4.5	.16	4.0	4.1	18	.18	4.7	0.041	1.0	4.50	SPR	CG	N
0.437	11.10	S-1144	.38	9.5	.381	9.7	4.5	.78	.22	5.6	.99	4.4	.15	3.9	0.028	0.7	4.50	SST	C	N
0.437	11.10	3984	.41	10.3	.361	9.2	23	4.1	.21	5.3	4.9	22	.19	4.8	0.038	1.0	4.00	SPR	C	Z
0.437	11.10	S-876	.41	10.3	.355	9.0	34	6.0	.17	4.2	5.7	25	.15	3.8	0.041	1.0	3.75	SST	CG	N
0.437	11.10	3920	.44	11.1	.353	9.0	36	6.3	.18	4.6	6.5	29	.17	4.3	0.042	1.1	4.00	SPR	CG	Z
0.437	11.10	S-157	.44	11.1	.327	8.3	104	18	.12	3.1	13	56	.22	5.6	0.055	1.4	4.00	SST	CG	N
0.437	11.10	S-196	.44	11.1	.327	8.3	69	12	.11	2.7	7.5	33	.33	8.4	0.055	1.4	5.00	SST	C	N
0.437	11.10	JJ-30	.47	11.9	.377	9.6	6.1	1.1	.33	8.5	2.0	9.1	.14	3.4	0.030	0.8	4.50	SST	CG	N
0.437	11.10	N-84	.47	11.9	.369	9.4	10	1.8	.28	7.1	2.8	13	.19	4.7	0.034	0.9	4.50	SST	C	N
0.437	11.10	FF-60	.47	11.9	.337	8.6	45	7.8	.21	5.5	9.6	43	.25	6.4	0.050	1.3	5.00	SST	CG	N
0.437	11.10	WW-68	.47	11.9	.313	8.0	133	23	.14	3.6	19	85	.31	7.9	0.062	1.6	5.00	SPR	CG	Z
0.437	11.10	2659	.47	11.9	.311	7.9	143	25	.14	3.5	20	89	.32	8.0	0.063	1.6	5.00	SPR	CG	Z
0.437	11.10	S-1039	.47	11.9	.277	7.0	446	78	.08	2.0	35	157	.36	9.1	0.080	2.0	4.50	SST	CG	N
0.437	11.10	11219	.50	12.7	.411	10.4	.12	.02	.41	10	.05	.22	.09	2.3	0.013	0.3	6.00	SST	C	N
0.437	11.10	TT-43	.50	12.7	.397	10.1	.91	.16	.38	9.7	.35	1.5	.12	3.0	0.020	0.5	5.00	SST	C	N
0.437	11.10	2989	.50	12.7	.377	9.6	8.6	1.5	.35	8.9	3.0	13	.15	3.8	0.030	0.8	4.00	MW	C	Z
0.437	11.10	12661	.50	12.7	.377	9.6	7.5	1.3	.31	8.0	2.4	10	.15	3.8	0.030	0.8	4.00	SST	C	N
0.437	11.10	10250	.50	12.7	.367	9.3	15	2.6	.26	6.6	3.8	17	.18	4.7	0.035	0.9	4.25	SPR	C	Z
0.437	11.10	AA-88	.50	12.7	.357	9.1	17	3.0	.30	7.6	5.1	23	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.437	11.10	K-25	.50	12.7	.355	9.0	28	4.9	.20	5.1	5.7	25	.21	5.2	0.041	1.0	4.00	SST	C	N
0.437	11.10	S-1557	.50	12.7	.337	8.6	54	9.4	.18	4.5	9.6	43	.23	5.7	0.050	1.3	4.50	SST	CG	N
0.437	11.10	B9-21	.50	12.7	.287	7.3	274	48	.09	2.2	24	107	.41	10.5	0.075	1.9	5.50	SPR	CG	N
0.437	11.10	S-3172	.53	13.5	.391	9.9	1.4	.24	.38	9.7	.53	2.4	.15	3.8	0.023	0.6	5.50	SST	C	N
0.437	11.10	B-48	.53	13.5	.363	9.2	15	2.5	.31	7.9	4.5	20	.18	4.6	0.037	0.9	5.00	SPR	CG	N
0.437	11.10	4206	.53	13.5	.293	7.4	263	46	.11	2.7	28	124	.36	9.1	0.072	1.8	5.00	SPR	CG	Z
0.437	11.10	11182	.56	14.3	.387	9.8	1.6	.28	.36	9.2	.58	2.6	.20	5.1	0.025	0.6	7.00	MW	C	N
0.437	11.10	3371	.56	14.3	.373	9.5	10	1.8	.31	7.8	3.1	14	.17	4.3	0.032	0.8	4.25	HD	C	Z
0.437	11.10	B-88	.56	14.3	.327	8.3	70	12	.18	4.6	13	56	.28	7.0	0.055	1.4	5.00	SST	CG	N
0.437	11.10	2993	.56	14.3	.313	8.0	133	23	.14	3.6	19	85	.31	7.9	0.062	1.6	5.00	SPR	CG	Z
0.437	11.10	4309	.56	14.3	.303	7.7	142	25	.16	4.1	23	101	.40	10.2	0.067	1.7	6.00	SPR	CG	Z
0.437	11.10	4275	.59	15.1	.313	8.0	100	17	.19	4.9	19	85	.37	9.4	0.062	1.6	6.00	SPR	CG	Z
0.437	11.10	S-1063	.63	15.9	.381	9.7	5.6	.98	.34	8.7	1.9	8.5	.14	3.6	0.028	0.7	4.00	SST	C	N
0.437	11.10	S-3062	.63	15.9	.373	9.5	9.8	1.7	.29	7.4	2.8	13	.16	4.1	0.032	0.8	4.00	SST	C	N
0.437	11.10	B11-67	.63	15.9	.373	9.5	11	2.0	.27	6.9	3.1	14	.13	3.3	0.032	0.8	4.00	SPR	CG	N
0.437	11.10	A12-6	.63	15.9	.359	9.1	18	3.1	.30	7.6	5.2	23	.23	5.9	0.039	1.0	5.00	SPR	C	N
0.437	11.10	2517	.63	15.9	.343	8.7	30	5.2	.31	7.8	9.1	40	.28	7.2	0.047	1.2	6.00	SPR	CG	Z
0.437	11.10	G-78	.63	15.9	.325	8.3	114	20	.12	3.2	14	63	.24	6.0	0.056	1.4	4.25	SPR	CG	N
0.437	11.10	JJ-64	.66	16.7	.405	10.3	.28	.05	.54	14	.15	.66	.12	3.0	0.016	0.4	6.50	MW	C	Z
0.437	11.10	S-897	.66	16.7	.385	9.8	2.1	.36	.50	13	1.0	4.6	.16	4.0	0.026	0.7	6.00	SST	CG	N
0.437	11.10	A11-48	.66	16.7	.345	8.8	33	5.8	.24	6.2	8.0	36	.27	6.9	0.046	1.2	5.00	SST	C	N
0.437	11.10	A11-69	.69	17.4	.287	7.3	317	56	.10	2.5	31	140	.38	9.5	0.075	1.9	5.00	SPR	CG	Z
0.437	11.10	12513	.69	17.5	.337	8.6	48	8.4	.30	7.5	14	63	.31	8.0	0.050	1.3	5.25	MW	C	N
0.437	11.10	S-128	.75	19.1	.397	10.1	.68	.12	.61	15	.42	1.9	.14	3.6	0.020	0.5	6.00	SST	C	N
0.437	11.10	S-920	.75	19.1	.385	9.8	1.6	.29	.54	14	.89	3.9	.21	5.3	0.026	0.7	7.00	SST	C	N
0.437	11.10	913	.75	19.1	.381	9.7	4.3	.75	.58	15	2.5	11	.17	4.3	0.028	0.7	5.00	MW	C	Z
0.437	11.10	11397	.75	19.1	.377	9.6	5.8	1.0	.57	14	3.3	15	.18	4.6	0.030	0.8	5.00	MW	C	Z
0.437	11.10	10795	.75	19.1	.367	9.3	7.4	1.3	.48	12	3.6	16	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.437	11.10	3977	.75	19.1	.367	9.3	9.4	1.6	.40	10	3.8	17	.19	4.9	0.035	0.9	5.50	SPR	CG	Z
0.437	11.10	S-1031	.75	19.1	.361	9.2	12	2.0	.39	9.9	4.6	20	.21	5.3	0.038	1.0	5.50	SST	CG	N
0.437	11.10	3791	.75	19.1	.353	9.0	29	5.0	.23	5.8	6.5	29	.23	5.9	0.042	1.1	4.50	SPR	C	Z
0.437	11.10	S-745	.75	19.1	.353	9.0	18	3.1	.34	8.7	6.1	27	.27	6.9	0.042	1.1	5.50	SST	C	N
0.437	11.10	10253	.75	19.1	.331	8.4	40	7.0	.30	7.7	12	54	.42	10.8	0.053	1.3	7.00	SPR	C	Z
0.437	11.10	513	.75	19.1	.329	8.4	48	8.4	.27	6.8	13	57	.41	10.3	0.054	1.4	6.50	HD	C	Z</



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEF.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.437	11.10	UU-66	.88	22.2	.313	8.0	80	14	.24	6.1	19	85	.43	11.0	0.062	1.6	7.00	HD	CG	Z
0.437	11.10	3212	.88	22.2	.293	7.4	158	28	.18	4.5	28	124	.50	12.8	0.072	1.8	7.00	SPR	CG	Z
0.437	11.10	S-1352	.88	22.2	.277	7.0	223	39	.16	4.0	35	157	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.437	11.10	S-1374	.91	23.0	.343	8.7	21	3.8	.40	10	8.5	38	.32	8.1	0.047	1.2	6.75	SST	CG	N
0.437	11.10	2582	.91	23.0	.327	8.3	43	7.5	.44	11	19	83	.41	10.5	0.055	1.4	7.50	MW	CG	Z
0.437	11.10	HH-100	.91	23.0	.293	7.4	108	19	.24	6.2	26	116	.61	15.5	0.072	1.8	8.50	SST	CG	N
0.437	11.10	A-74	.94	23.8	.397	10.1	.39	.07	.72	18	.28	1.3	.22	5.6	0.020	0.5	10.0	MW	C	BO
0.437	11.10	A-99	.94	23.8	.387	9.8	1.2	.20	.74	19	.85	3.8	.20	5.1	0.025	0.6	8.00	SST	CG	N
0.437	11.10	B10-3	.94	23.8	.373	9.5	4.5	.79	.67	17	3.1	14	.26	6.5	0.032	0.8	7.00	SPR	C	Z
0.437	11.10	S-848	.94	23.8	.367	9.3	5.8	1.0	.61	16	3.6	16	.25	6.2	0.035	0.9	7.00	SST	CG	N
0.437	11.10	U-63	.94	23.8	.353	9.0	14	2.5	.45	12	6.5	29	.29	7.5	0.042	1.1	7.00	SPR	CG	GI
0.437	11.10	S-787	.97	24.6	.381	9.7	2.2	.39	.77	20	1.7	7.7	.20	5.0	0.028	0.7	7.00	SST	CG	N
0.437	11.10	S-862	.97	24.6	.369	9.4	5.2	.91	.66	17	3.4	15	.27	6.8	0.034	0.9	7.00	SST	C	N
0.437	11.10	10206	1.00	25.4	.397	10.1	.39	.07	.78	20	.31	1.4	.22	5.6	0.020	0.5	10.0	MW	C	Z
0.437	11.10	S-1253	1.00	25.4	.389	9.9	1.5	.26	.83	21	1.2	5.4	.17	4.3	0.024	0.6	6.00	SST	C	N
0.437	11.10	MM-78	1.00	25.4	.381	9.7	2.5	.43	.77	20	1.9	8.5	.21	5.3	0.028	0.7	6.50	SST	C	N
0.437	11.10	1930	1.00	25.4	.377	9.6	3.5	.60	.76	19	2.6	12	.24	6.1	0.030	0.8	7.00	MW	C	Z
0.437	11.10	3996	1.00	25.4	.371	9.4	6.4	1.1	.52	13	3.4	15	.20	5.0	0.033	0.8	6.00	SPR	CG	Z
0.437	11.10	S-1059	1.00	25.4	.357	9.1	8.5	1.5	.63	16	5.3	24	.36	9.1	0.040	1.0	8.00	SST	C	N
0.437	11.10	HH-35	1.00	25.4	.357	9.1	12	2.0	.46	12	5.3	24	.26	6.6	0.040	1.0	6.50	SST	CG	N
0.437	11.10	S-747	1.00	25.4	.353	9.0	13	2.2	.49	12	6.1	27	.34	8.5	0.042	1.1	7.00	SST	C	N
0.437	11.10	EE-82	1.00	25.4	.353	9.0	9.0	1.6	.54	14	4.8	22	.46	11.7	0.042	1.1	10.0	SPR	C	Z
0.437	11.10	4151	1.00	25.4	.345	8.8	16	2.9	.52	13	8.5	38	.44	11.1	0.046	1.2	8.50	SPR	C	Z
0.437	11.10	943	1.00	25.4	.343	8.7	23	4.1	.39	9.8	9.1	40	.38	9.6	0.047	1.2	7.00	HD	C	Z
0.437	11.10	12657	1.00	25.4	.343	8.7	24	4.1	.53	14	13	56	.33	8.4	0.047	1.2	7.00	MW	CG	N
0.437	11.10	10936	1.00	25.4	.327	8.3	34	5.9	.40	10	13	60	.50	12.6	0.055	1.4	9.00	SPR	CG	N
0.437	11.10	S-751	1.00	25.4	.327	8.3	34	5.9	.37	9.5	13	56	.50	12.6	0.055	1.4	8.00	SST	C	N
0.437	11.10	Z-87	1.00	25.4	.305	7.7	77	13	.28	7.1	22	96	.53	13.4	0.066	1.7	8.00	SST	CG	N
0.437	11.10	J-19	1.00	25.4	.295	7.5	80	14	.29	7.4	23	104	.71	18.0	0.071	1.8	10.0	SST	CG	N
0.437	11.10	10312	1.00	25.4	.293	7.4	132	23	.21	5.4	28	124	.65	16.5	0.072	1.8	8.00	SPR	C	Z
0.437	11.10	A9-26	1.03	26.2	.397	10.1	.39	.07	.81	21	.32	1.4	.22	5.6	0.020	0.5	10.0	MW	C	BO
0.437	11.10	B10-31	1.03	26.2	.355	9.0	8.7	1.5	.60	15	5.2	23	.43	10.9	0.041	1.0	9.50	SPR	C	N
0.437	11.10	520	1.06	27.0	.355	9.0	11	2.0	.54	14	6.1	27	.36	9.1	0.041	1.0	7.75	HD	C	Z
0.437	11.10	Q-41	1.06	27.0	.347	8.8	14	2.5	.53	14	7.5	33	.36	9.1	0.045	1.1	8.00	SST	CG	N
0.437	11.10	3454	1.06	27.0	.313	8.0	53	9.3	.36	9.1	19	85	.59	15.0	0.062	1.6	9.50	HD	CG	Z
0.437	11.10	509	1.06	27.0	.313	8.0	80	14	.24	6.1	19	85	.50	12.6	0.062	1.6	7.00	HD	C	Z
0.437	11.10	3534	1.06	27.0	.311	7.9	78	14	.36	9.0	28	123	.47	12.0	0.063	1.6	7.50	MW	CG	Z
0.437	11.10	10862	1.06	27.0	.295	7.5	110	19	.23	5.8	25	112	.64	16.2	0.071	1.8	8.00	SST	C	N
0.437	11.10	10765	1.08	27.4	.369	9.4	3.6	.64	.74	19	2.7	12	.34	8.6	0.034	0.9	10.0	SPR	CG	Z
0.437	11.10	10480	1.09	27.8	.393	10.0	1.3	.24	.95	24	1.3	5.7	.14	3.6	0.022	0.6	5.50	MW	C	N
0.437	11.10	V-3	1.09	27.8	.377	9.6	3.1	.54	.77	19	2.4	10	.24	6.1	0.030	0.8	7.00	SST	C	N
0.437	11.10	B15-70	1.09	27.8	.359	9.1	5.3	.92	.63	16	3.3	15	.47	11.9	0.039	1.0	12.0	SPR	CG	N
0.437	11.10	S-1164	1.13	28.6	.377	9.6	3.0	.52	.79	20	2.4	10	.24	6.1	0.030	0.8	7.00	SST	C	N
0.437	11.10	10762	1.13	28.6	.343	8.7	24	4.1	.38	9.8	9.1	40	.33	8.4	0.047	1.2	7.00	SPR	CG	Z
0.437	11.10	B9-61	1.13	28.6	.343	8.7	19	3.3	.45	11	8.5	38	.40	10.1	0.047	1.2	7.50	SST	C	N
0.437	11.10	11126	1.13	28.6	.307	7.8	100	17	.22	5.6	22	97	.52	13.2	0.065	1.7	7.00	SPR	C	Z
0.437	11.10	J-60	1.13	28.6	.293	7.4	105	18	.27	6.8	28	124	.68	17.4	0.072	1.8	9.50	SPR	CG	Z
0.437	11.10	12295	1.16	29.4	.345	8.8	12	2.1	.60	15	7.2	32	.55	14.0	0.046	1.2	11.0	SPR	C	Z
0.437	11.10	3725	1.16	29.4	.327	8.3	28	4.8	.49	12	13	60	.58	14.7	0.055	1.4	10.5	SPR	CG	Z
0.437	11.10	S-1679	1.16	29.4	.251	6.4	293	51	.18	4.5	51	229	.93	23.6	0.093	2.4	10.0	SST	CG	N
0.437	11.10	Q0-56	1.19	30.2	.369	9.4	4.9	.85	.88	22	4.3	19	.31	7.8	0.034	0.9	8.00	MW	C	GI
0.437	11.10	10883	1.19	30.2	.313	8.0	57	9.9	.32	8.0	18	80	.51	13.0	0.062	1.6	8.25	SST	CG	N
0.437	11.10	S-1467	1.25	31.8	.355	9.0	10	1.8	.56	14	5.7	25	.31	7.8	0.041	1.0	7.50	SST	CG	N
0.437	11.10	3166	1.25	31.8	.353	9.0	6.7	1.2	.67	17	4.5	20	.58	14.7	0.042	1.1	12.8	SPR	C	Z
0.437	11.10	S-748	1.25	31.8	.353	9.0	9.6	1.7	.63	16	6.1	27	.40	10.1	0.042	1.1	8.50	SST	C	N
0.437	11.10	10202	1.25	31.8	.347	8.8	16	2.9	.49	12	8.0	36	.36	9.1	0.045	1.1	8.00	SPR	CG	Z
0.437	11.10	S-409	1.25	31.8	.343	8.7	7.8	1.4	.55	14	4.3	19	.71	17.9	0.047	1.2	15.0	SST	CG	N
0.437	11.10	S-1297	1.25	31.8	.329	8.4	26	4.5	.46	12	12	53	.50	12.7	0.054	1.4	9.25	SST	CG	N
0.437	11.10	S-752	1.25	31.8	.327	8.3	26	4.6	.48	12	13	56	.59	15.0	0.055	1.4	9.75	SST	C	N
0.437	11.10	11337	1.25	31.8	.313	8.0	45	7.8	.40	10	18	80	.62	15.7	0.062	1.6	10.0	SST	CG	N
0.437	11.10	N-133	1.25	31.8	.309	7.8	51	9.0	.41	10	21	93	.70	17.9	0.064	1.6	11.0	SPR	CG	Z
0.437	11.10	S-810	1.25	31.8	.293	7.4	76	13	.34	8.7	26	116	.79	20.1	0.072	1.8	11.0	SST	CG	N
0.437	11.10	A11-3	1.31	33.3	.363	9.2	1.8	.32	.78	20	1.4	6.3	.54	13.6	0.037	0.9	14.5	PB	CG	N
0.437	11.10	K-60	1.31	33.3	.343	8.7	23	4.1	.39	9.8	9.1	40	.33	8.4	0.047	1.2	7.00	SPR	CG	N
0.437	11.10	3598	1.34	34.1	.377	9.6	1.4	.24	.88	22	1.2	5.4	.47	11.8	0.030	0.8	14.5	MW	C	Z
0.437	11.10	A13-36	1.34	34.1	.359	9.1	9.1	1.6	.58	15	5.2	23	.34	8.7	0.039	1.0	7.75	SPR	C	N
0.437	11.10	1892	1.34	34.1	.313	8.0	45	7.8	.59	15	26	118	.68	17.3	0.062	1.6	11.0	MW	CG	Z
0.437	11.10	12118	1.34	34.1	.309	7.8	46	8.1	.45	11	21	93	.77	19.5	0.064	1.6	12.0	SPR	CG	Z
0.437	11.10	A11-53	1.38	34.9	.347															




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.437	11.10	A-55	1.44	36.5	.297	7.5	73	13	.35	9.0	26	115	.81	20.4	0.070	1.8	11.5	SPR	CG	N
0.437	11.10	J-24	1.50	38.1	.399	10.1	.44	.08	1.3	34	.60	2.7	.15	3.9	0.019	0.5	7.00	SST	C	N
0.437	11.10	1753	1.50	38.1	.397	10.1	.71	.12	1.4	34	.95	4.2	.15	3.8	0.020	0.5	6.50	MW	CG	Z
0.437	11.10	12223	1.50	38.1	.365	9.3	5.8	1.0	.72	18	4.1	18	.31	7.8	0.036	0.9	8.50	SPR	CG	GI
0.437	11.10	S-749	1.50	38.1	.353	9.0	8.1	1.4	.76	19	6.1	27	.45	11.5	0.042	1.1	9.75	SST	C	N
0.437	11.10	S-1295	1.50	38.1	.349	8.9	10	1.8	.69	17	7.0	31	.42	10.6	0.044	1.1	9.50	SST	CG	N
0.437	11.10	A11-36	1.50	38.1	.347	8.8	13	2.3	.62	16	8.0	36	.43	10.9	0.045	1.1	9.50	SPR	CG	N
0.437	11.10	CC-10	1.50	38.1	.337	8.6	21	3.6	.49	13	10	45	.48	12.1	0.050	1.3	9.50	SPR	CG	N
0.437	11.10	S-753	1.50	38.1	.327	8.3	21	3.8	.59	15	13	56	.63	16.1	0.055	1.4	11.5	SST	CG	N
0.437	11.10	B11-54	1.50	38.1	.325	8.3	27	4.7	.53	13	14	63	.70	17.8	0.056	1.4	11.5	SPR	C	Z
0.437	11.10	10262	1.50	38.1	.293	7.4	88	15	.32	8.0	28	124	.79	20.1	0.072	1.8	11.0	SPR	CG	Z
0.437	11.10	3273	1.50	38.1	.253	6.4	262	46	.21	5.2	54	239	1.06	26.9	0.092	2.3	11.5	SPR	CG	Z
0.437	11.10	12423	1.56	39.7	.401	10.2	.46	.08	1.4	36	.65	2.9	.14	3.4	0.018	0.5	6.50	MW	C	GI
0.437	11.10	10129	1.56	39.7	.355	9.0	8.7	1.5	.70	18	6.1	27	.43	10.9	0.041	1.0	9.50	SPR	C	Z
0.437	11.10	10895	1.56	39.7	.345	8.8	11	1.9	.80	20	8.5	38	.60	15.2	0.046	1.2	12.0	SPR	C	Z
0.437	11.10	10232	1.63	41.3	.397	10.1	.63	.11	1.5	37	.93	4.1	.16	4.1	0.020	0.5	7.00	MW	C	Z
0.437	11.10	10126	1.63	41.3	.393	10.0	.94	.16	1.4	37	1.4	6.1	.18	4.5	0.022	0.6	7.00	MW	C	Z
0.437	11.10	S-1379	1.63	41.3	.393	10.0	.63	.11	1.4	36	.89	3.9	.21	5.3	0.022	0.6	8.50	SST	C	N
0.437	11.10	00-77	1.63	41.3	.337	8.6	12	2.1	.85	22	10	45	.75	19.1	0.050	1.3	15.0	SPR	CG	N
0.437	11.10	10752	1.66	42.1	.293	7.4	83	15	.34	8.6	28	124	.83	21.0	0.072	1.8	11.5	SPR	CG	GI
0.437	11.10	12428	1.69	42.8	.387	9.8	.94	.17	1.4	36	1.3	5.9	.29	7.3	0.025	0.6	10.5	MW	C	N
0.437	11.10	3123	1.69	42.8	.385	9.8	1.1	.19	1.4	35	1.5	6.8	.30	7.6	0.026	0.7	10.5	MW	C	GI
0.437	11.10	S-1274	1.69	42.8	.375	9.5	2.4	.43	1.1	27	2.6	12	.31	7.9	0.031	0.8	9.00	SST	C	N
0.437	11.10	B11-27	1.69	42.8	.337	8.6	39	6.8	.26	6.7	10	45	.30	7.6	0.050	1.3	6.00	SPR	CG	N
0.437	11.10	TT-56	1.69	42.8	.287	7.3	86	15	.36	9.2	31	140	.98	24.8	0.075	1.9	13.0	SPR	CG	Z
0.437	11.10	10767	1.75	44.5	.361	9.2	3.4	.59	1.1	29	3.8	17	.61	15.4	0.038	1.0	16.0	SPR	CG	N
0.437	11.10	4154	1.75	44.5	.287	7.3	79	14	.40	10	31	140	1.13	28.6	0.075	1.9	14.0	SPR	C	Z
0.437	11.10	10374	1.78	45.2	.267	6.8	146	26	.31	7.8	45	199	1.17	29.7	0.085	2.2	13.8	SPR	CG	Z
0.437	11.10	10389	1.81	46.0	.389	9.9	.82	.14	1.5	39	1.3	5.6	.27	6.9	0.024	0.6	10.3	MW	C	N
0.437	11.10	112	1.88	47.6	.369	9.4	3.1	.54	1.2	30	3.7	16	.43	10.8	0.034	0.9	11.5	HD	C	Z
0.437	11.10	4163	1.88	47.6	.357	9.1	6.5	1.1	.87	22	5.7	25	.48	12.2	0.040	1.0	11.0	SPR	C	Z
0.437	11.10	KK-78	1.88	47.6	.217	5.5	860	151	.10	2.5	85	378	.99	25.1	0.110	2.8	9.00	SPR	CG	Z
0.437	11.10	Q-49	1.94	49.2	.327	8.3	13	2.3	.85	22	11	50	1.09	27.6	0.055	1.4	19.8	SPR	CG	GI
0.437	11.10	3652	2.00	50.8	.375	9.5	1.4	.25	1.5	37	2.1	9.2	.53	13.4	0.031	0.8	16.0	HD	C	Z
0.437	11.10	S-854	2.00	50.8	.343	8.7	6.6	1.2	1.1	29	7.4	33	.87	22.1	0.047	1.2	17.5	SST	C	N
0.437	11.10	16	2.00	50.8	.329	8.4	16	2.8	.79	20	13	57	.89	22.6	0.054	1.4	15.5	HD	C	Z
0.437	11.10	S-1154	2.00	50.8	.329	8.4	14	2.5	.83	21	12	53	.86	21.9	0.054	1.4	15.0	SST	C	N
0.437	11.10	3553	2.00	50.8	.323	8.2	15	2.7	.86	22	13	58	1.14	29.0	0.057	1.4	20.0	MW	CG	Z
0.437	11.10	502	2.00	50.8	.293	7.4	52	9.0	.54	14	28	124	1.31	33.4	0.072	1.8	17.3	HD	C	Z
0.437	11.10	527	2.13	54.0	.375	9.5	2.3	.42	1.4	35	2.8	12	.41	10.5	0.032	0.8	11.8	HD	C	Z
0.437	11.10	2527	2.13	54.0	.353	9.0	6.0	1.1	1.1	27	6.5	29	.63	16.0	0.042	1.1	14.0	SPR	C	Z
0.437	11.10	4248	2.25	57.2	.389	9.9	.48	.08	1.8	47	.88	3.9	.41	10.4	0.024	0.6	16.0	MW	C	Z
0.437	11.10	13	2.25	57.2	.355	9.0	4.9	.86	1.2	31	6.1	27	.67	16.9	0.041	1.0	15.3	HD	C	Z
0.437	11.10	S-840	2.44	61.9	.297	7.5	33	5.8	.73	19	24	107	1.42	36.0	0.070	1.8	20.3	SST	CG	N
0.437	11.10	2816	2.47	62.7	.295	7.5	40	7.1	.93	24	37	167	1.44	36.5	0.071	1.8	20.3	MW	CG	Z
0.437	11.10	11334	2.50	63.5	.341	8.7	8.9	1.6	1.1	27	9.7	43	.84	21.3	0.048	1.2	16.5	HD	C	Z
0.437	11.10	11889	2.50	63.5	.313	8.0	26	4.6	.73	19	19	85	1.09	27.6	0.062	1.6	17.5	SPR	CG	Z
0.437	11.10	3728	2.50	63.5	.277	7.0	66	12	.57	15	38	168	1.72	43.7	0.080	2.0	21.5	SPR	CG	Z
0.437	11.10	12452	2.59	65.9	.341	8.7	7.2	1.3	1.3	34	9.7	43	.96	24.4	0.048	1.2	20.0	SPR	CG	N
0.437	11.10	10403	2.75	69.9	.375	9.5	1.3	.22	2.2	55	2.8	12	.57	14.6	0.031	0.8	17.5	MW	C	Z
0.437	11.10	11968	2.78	70.6	.325	8.3	13	2.4	1.1	27	14	63	1.23	31.3	0.056	1.4	21.0	SPR	C	Z
0.437	11.10	2552	2.88	73.0	.285	7.2	46	8.1	.70	18	33	145	1.82	46.3	0.076	1.9	24.0	SPR	CG	Z
0.437	11.10	4150	3.00	76.2	.343	8.7	9.0	1.6	1.0	26	9.1	40	.75	19.1	0.047	1.2	15.0	HD	C	Z
0.437	11.10	4152	3.13	79.4	.313	8.0	22	3.9	.86	22	19	85	1.30	33.1	0.062	1.6	20.0	HD	C	Z
0.437	11.10	3217	3.22	81.8	.293	7.4	32	5.5	.89	23	28	124	1.94	49.4	0.072	1.8	27.0	SPR	CG	Z
0.437	11.10	10180	3.38	85.7	.321	8.2	10	1.7	1.5	39	15	67	1.86	47.1	0.058	1.5	32.0	SPR	CG	Z
0.437	11.10	2965	3.44	87.3	.357	9.1	2.3	.41	2.3	59	5.4	24	1.12	28.4	0.040	1.0	27.0	MW	C	Z
0.437	11.10	3690	3.44	87.3	.323	8.2	8.6	1.5	1.5	38	13	57	1.94	49.2	0.057	1.4	34.0	SPR	CG	Z
0.437	11.10	1928	3.75	95.3	.297	7.5	35	6.1	.74	19	26	115	1.54	39.1	0.070	1.8	22.0	SPR	CG	Z
0.437	11.10	10089	3.75	95.3	.287	7.3	38	6.7	.83	21	31	140	2.03	51.4	0.075	1.9	27.0	SPR	CG	Z
0.437	11.10	12476	4.25	108.0	.289	7.3	28	4.9	1.1	27	30	134	2.59	65.8	0.074	1.9	34.0	SPR	C	Z
0.437	11.10	12085	5.00	127.0	.357	9.1	1.8	.32	3.1	78	5.7	25	1.36	34.5	0.040	1.0	34.0	SPR	CG	Z
0.437	11.10	10098	5.00	127.0	.343	8.7	3.4	.59	2.7	69	9.1	40	1.79	45.4	0.047	1.2	37.0	SPR	C	Z
0.437	11.10	11490	5.16	131.0	.341	8.7	3.7	.64	2.6	67	9.7	43	1.84	46.6	0.048	1.2	37.3	SPR	C	Z
0.437	11.10	S-1685	6.25	158.8	.309	7.8	12	2.1	1.6	41	20	88	2.32	58.9	0.064	1.6	35.3	SST	C	N
0.437	11.10	1641	8.63	219.1	.343	8.7	2.4	.42	5.3	134	13	56	2.42	61.5	0.047	1.2	51.5	MW	CG	GI
0.443	11.25	12795	1.44	36.5	.347	8.8	10	1.8	.72	18	7.4	33	.72	18.3	0.048	1.2	14.0	MW	C	Z</



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEF.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.453	11.51	B1-6	.50	12.7	.341	8.7	90	16	.15	3.9	14	61	.25	6.4	0.056	1.4	4.50	SPR	CG	GI
0.453	11.51	RR-16	.50	12.7	.341	8.7	70	12	.20	5.0	14	61	.29	7.5	0.056	1.4	5.25	SPR	CG	N
0.453	11.51	K-80	.53	13.5	.383	9.7	12	2.1	.31	7.9	3.7	16	.16	4.0	0.035	0.9	4.50	SPR	CG	N
0.453	11.51	JJ-2	.53	13.5	.373	9.5	17	3.0	.31	8.0	5.5	24	.20	5.1	0.040	1.0	5.00	SPR	CG	N
0.453	11.51	12517	.56	14.3	.389	9.9	8.1	1.4	.39	9.8	3.1	14	.18	4.5	0.032	0.8	4.50	MW	C	Z
0.453	11.51	B1-31	.56	14.3	.363	9.2	35	6.1	.22	5.7	7.7	34	.20	5.1	0.045	1.1	4.50	SPR	CG	N
0.453	11.51	U-60	.56	14.3	.345	8.8	59	10	.21	5.3	12	55	.28	7.2	0.054	1.4	5.25	SPR	CG	N
0.453	11.51	1767	.56	14.3	.337	8.6	88	15	.24	6.1	21	94	.29	7.4	0.058	1.5	5.00	MW	CG	Z
0.453	11.51	S-1098	.56	14.3	.325	8.3	102	18	.19	4.8	19	85	.35	8.9	0.064	1.6	5.50	SST	CG	N
0.453	11.51	S-1472	.59	15.1	.379	9.6	13	2.3	.31	7.9	4.1	18	.20	5.2	0.037	0.9	4.50	SST	C	N
0.453	11.51	PP-93	.63	15.9	.397	10.1	2.6	.45	.42	11	1.1	4.7	.21	5.3	0.028	0.7	6.50	MW	C	N
0.453	11.51	N-105	.63	15.9	.391	9.9	5.1	.90	.47	12	2.4	11	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.453	11.51	B10-67	.63	15.9	.381	9.7	17	2.9	.24	6.1	4.0	18	.14	3.7	0.036	0.9	4.00	SPR	CG	Z
0.453	11.51	K-40	.63	15.9	.377	9.6	15	2.6	.30	7.7	4.4	20	.17	4.3	0.038	1.0	4.50	SST	CG	N
0.453	11.51	B7-17	.63	15.9	.373	9.5	19	3.3	.29	7.3	5.5	24	.19	4.8	0.040	1.0	4.75	SPR	CG	Z
0.453	11.51	A14-42	.63	15.9	.367	9.3	18	3.1	.37	9.3	6.5	29	.26	6.6	0.043	1.1	6.00	SPR	CG	GI
0.453	11.51	A11-61	.66	16.7	.321	8.2	118	21	.19	4.8	22	99	.40	10.1	0.066	1.7	6.00	SPR	CG	Z
0.453	11.51	YY-66	.69	17.4	.417	10.6		.32	.54	14	.17	.77	.14	3.7	0.018	0.5	7.00	SST	C	N
0.453	11.51	A14-30	.69	17.4	.377	9.6	12	2.2	.35	9.0	4.4	20	.19	4.8	0.038	1.0	5.00	SST	CG	N
0.453	11.51	B12-19	.72	18.2	.389	9.9	5.8	1.0	.51	13	2.9	13	.21	5.3	0.032	0.8	5.50	SPR	C	N
0.453	11.51	B14-49	.72	18.2	.369	9.4	21	3.8	.29	7.5	6.3	28	.21	5.3	0.042	1.1	5.00	SPR	CG	Z
0.453	11.51	S-3174	.75	19.1	.409	10.4		.46	.51	13	.23	1.0	.24	6.1	0.022	0.6	10.0	SST	C	N
0.453	11.51	B14-54	.75	19.1	.381	9.7	8.4	1.5	.44	11	3.7	17	.20	5.0	0.036	0.9	5.50	SST	CG	N
0.453	11.51	A14-32	.75	19.1	.375	9.5	16	2.7	.32	8.2	5.1	23	.20	5.0	0.039	1.0	5.00	SPR	CG	N
0.453	11.51	10072	.75	19.1	.371	9.4	15	2.5	.40	10	5.9	26	.29	7.3	0.041	1.0	6.00	SPR	C	Z
0.453	11.51	A13-55	.75	19.1	.363	9.2	22	3.9	.33	8.4	7.2	32	.25	6.3	0.045	1.1	5.50	SST	CG	N
0.453	11.51	10227	.75	19.1	.351	8.9	30	5.2	.35	8.9	10	46	.36	9.1	0.051	1.3	7.00	SPR	CG	Z
0.453	11.51	3441	.75	19.1	.345	8.8	35	6.1	.29	7.4	10	45	.46	11.7	0.054	1.4	7.50	SPR	C	Z
0.453	11.51	10055	.75	19.1	.341	8.7	56	9.9	.24	6.2	14	61	.39	10.0	0.056	1.4	6.00	SPR	C	GI
0.453	11.51	FF-64	.75	19.1	.333	8.5	77	13	.22	5.6	17	75	.36	9.1	0.060	1.5	6.00	SPR	CG	N
0.453	11.51	1952	.78	19.8	.401	10.2	2.8	.49	.63	16	1.8	7.8	.16	4.0	0.026	0.7	5.00	MW	C	Z
0.453	11.51	M-144	.78	19.8	.389	9.9	3.3	.57	.51	13	1.7	7.4	.27	6.9	0.032	0.8	7.50	SST	C	N
0.453	11.51	B1-40	.78	19.8	.367	9.3	22	3.8	.31	7.8	6.8	30	.23	5.7	0.043	1.1	5.25	SPR	CG	N
0.453	11.51	S-1434	.81	20.6	.371	9.4	14	2.5	.38	9.7	5.5	24	.23	5.7	0.041	1.0	5.50	SST	CG	N
0.453	11.51	3907	.81	20.6	.345	8.8	32	5.6	.33	8.3	10	47	.49	12.3	0.054	1.4	8.00	SPR	C	Z
0.453	11.51	H-91	.88	22.2	.423	10.7		.06	.64	16	.04	.16	.24	6.1	0.015	0.4	15.0	SST	C	N
0.453	11.51	12424	.88	22.2	.407	10.3		1.7	.74	19	1.2	5.5	.14	3.5	0.023	0.6	5.00	MW	C	GI
0.453	11.51	S-1191	.88	22.2	.393	10.0	2.2	.39	.61	15	1.3	6.0	.27	6.9	0.030	0.8	8.00	SST	C	N
0.453	11.51	PP-24	.88	22.2	.393	10.0	1.3	.22	.46	12	.58	2.6	.42	10.7	0.030	0.8	14.0	MW	CG	N
0.453	11.51	LL-97	.88	22.2	.377	9.6	10	1.8	.42	11	4.4	20	.25	6.3	0.038	1.0	5.50	SST	C	N
0.453	11.51	10143	.88	22.2	.369	9.4	16	2.8	.39	10	6.3	28	.25	6.4	0.042	1.1	6.00	SPR	CG	Z
0.453	11.51	K-36	.88	22.2	.367	9.3	14	2.5	.47	12	6.8	30	.30	7.6	0.043	1.1	7.00	SPR	CG	Z
0.453	11.51	A11-34	.88	22.2	.363	9.2	20	3.6	.38	9.6	7.7	34	.28	7.1	0.045	1.1	6.25	SPR	CG	GI
0.453	11.51	A13-42	.88	22.2	.361	9.2	21	3.6	.38	9.6	7.7	34	.28	7.2	0.046	1.2	6.00	SST	CG	N
0.453	11.51	CC-35	.88	22.2	.353	9.0	27	4.8	.36	9.1	9.8	44	.40	10.2	0.050	1.3	7.00	SPR	C	Z
0.453	11.51	DD-22	.88	22.2	.353	9.0	24	4.3	.38	9.7	9.3	41	.35	8.9	0.050	1.3	7.00	SST	CG	N
0.453	11.51	QQ-70	.88	22.2	.351	8.9	25	4.4	.42	11	10	46	.41	10.4	0.051	1.3	8.00	SPR	CG	Z
0.453	11.51	A14-45	.88	22.2	.343	8.7	39	6.8	.31	8.0	12	54	.37	9.4	0.055	1.4	6.75	SST	CG	N
0.453	11.51	10746	.88	22.2	.329	8.4	53	9.2	.33	8.4	17	77	.50	12.6	0.062	1.6	8.00	SST	CG	N
0.453	11.51	1761	.91	23.0	.407	10.3		1.7	.77	20	1.3	5.8	.14	3.5	0.023	0.6	5.00	MW	C	Z
0.453	11.51	12417	.94	23.8	.407	10.3		1.7	.80	20	1.3	6.0	.14	3.5	0.023	0.6	5.00	MW	C	N
0.453	11.51	12435	.94	23.8	.405	10.3		2.0	.79	20	1.6	7.1	.14	3.7	0.024	0.6	5.00	MW	C	N
0.453	11.51	A13-27	.94	23.8	.377	9.6	11	1.9	.43	11	4.7	21	.22	5.7	0.038	1.0	6.00	SPR	CG	N
0.453	11.51	10194	1.00	25.4	.419	10.6		.41	.89	23	.37	1.6	.11	2.8	0.017	0.4	5.50	MW	N	N
0.453	11.51	LL-54	1.00	25.4	.409	10.4		.56	.77	20	.43	1.9	.23	5.9	0.022	0.6	9.50	MW	C	Z
0.453	11.51	S-93	1.00	25.4	.403	10.2	2.1	.36	.64	16	1.3	5.9	.13	3.2	0.025	0.6	5.00	SST	CG	N
0.453	11.51	2830	1.00	25.4	.395	10.0	2.7	.47	.77	20	2.0	9.1	.23	5.9	0.029	0.7	7.00	MW	C	Z
0.453	11.51	N-142	1.00	25.4	.393	10.0	2.2	.39	.73	19	1.6	7.2	.27	6.9	0.030	0.8	8.00	SST	C	N
0.453	11.51	10215	1.00	25.4	.391	9.9	3.9	.69	.80	20	3.1	14	.20	5.1	0.031	0.8	6.50	MW	CG	GI
0.453	11.51	A14-58	1.00	25.4	.375	9.5	10	1.8	.46	12	4.8	21	.23	5.9	0.039	1.0	6.00	SST	CG	N
0.453	11.51	3765	1.00	25.4	.373	9.5	6.5	1.1	.60	15	3.9	17	.40	10.2	0.040	1.0	10.0	SPR	CG	Z
0.453	11.51	10085	1.00	25.4	.371	9.4	14	2.4	.43	11	5.9	26	.26	6.5	0.041	1.0	6.25	SPR	CG	GI
0.453	11.51	B1-60	1.00	25.4	.361	9.2	17	3.0	.46	12	7.7	34	.32	8.2	0.046	1.2	7.00	SST	CG	N
0.453	11.51	TT-60	1.00	25.4	.319	8.1	72	13	.32	8.2	23	103	.60	15.3	0.067	1.7	9.00	SPR	CG	GI
0.453	11.51	00-16	1.00	25.4	.293	7.4	168	29	.20	5.2	34	153	.64	16.3	0.080	2.0	8.00	SST	CG	N
0.453	11.51	A11-46	1.03	26.2	.369	9.4	12	2.1	.48	12	5.9	26	.28	7.1	0.042	1.1	6.75	SST	CG	N
0.453	11.51	A15-51	1.03	26.2	.343	8.7	36	6.4	.36	9.1	13	58	.43	10.8	0.055	1.4	7.75	SPR	CG	GI
0.453	11.51	H-50	1.06	27.0	.407	10.3		.66	.82	21	.54	2.4	.24	6.2	0.023	0.6	9.50	MW	C	Z
0.453	11.51	B12-35	1.06	27.0	.359	9.1	12	2.0	.55	14	6.3	28	.52	13.1	0.047					



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.453	11.51	A14-60	1.25	31.8	.369	9.4	9.5	1.7	.62	16	5.9	26	.34	8.5	0.042	1.1	8.00	SST	CG	N
0.453	11.51	S-1278	1.25	31.8	.363	9.2	13	2.2	.58	15	7.2	32	.41	10.3	0.045	1.1	8.00	SST	C	N
0.453	11.51	A11-41	1.25	31.8	.359	9.1	17	3.1	.50	13	8.8	39	.38	9.6	0.047	1.2	8.00	SPR	CG	GI
0.453	11.51	CC-93	1.25	31.8	.353	9.0	16	2.8	.57	14	9.3	41	.48	12.1	0.050	1.3	9.50	SST	CG	N
0.453	11.51	BB-81	1.25	31.8	.351	8.9	16	2.8	.60	15	9.8	44	.51	13.0	0.051	1.3	10.0	SST	CG	N
0.453	11.51	00-80	1.25	31.8	.333	8.5	38	6.7	.44	11	17	75	.60	15.2	0.060	1.5	10.0	SPR	CG	N
0.453	11.51	A14-27	1.25	31.8	.309	7.8	69	12	.37	9.4	25	113	.79	20.1	0.072	1.8	11.0	SST	CG	N
0.453	11.51	12414	1.28	32.5	.399	10.1	1.3	.24	1.0	26	1.4	6.1	.26	6.5	0.027	0.7	8.50	SST	C	N
0.453	11.51	12434	1.28	32.5	.395	10.0	2.1	.36	1.0	26	2.1	9.2	.28	7.0	0.029	0.7	8.50	MW	C	N
0.453	11.51	S-1601	1.28	32.5	.365	9.3	12	2.0	.58	15	6.8	30	.40	10.1	0.044	1.1	8.00	SST	CG	N
0.453	11.51	VW-42	1.28	32.5	.273	6.9	263	46	.19	4.7	49	219	.86	21.7	0.090	2.3	9.50	SPR	CG	Z
0.453	11.51	12651	1.31	33.3	.407	10.3	.88	.15	1.1	29	.99	4.4	.18	4.7	0.023	0.6	7.00	SST	CG	N
0.453	11.51	A11-70	1.31	33.3	.293	7.4	123	21	.30	7.6	37	163	.90	22.9	0.080	2.0	11.3	SPR	CG	Z
0.453	11.51	2849	1.34	34.1	.405	10.3	.81	.14	1.1	28	.88	3.9	.25	6.4	0.024	0.6	9.50	MW	C	Z
0.453	11.51	S-245	1.38	34.9	.361	9.2	13	2.3	.58	15	7.7	34	.38	9.6	0.046	1.2	8.25	SST	CG	N
0.453	11.51	3640	1.38	34.9	.345	8.8	26	4.5	.48	12	12	55	.51	13.0	0.054	1.4	9.50	SPR	CG	Z
0.453	11.51	S-453	1.38	34.9	.343	8.7	23	4.1	.52	13	12	54	.54	13.6	0.055	1.4	9.75	SST	CG	N
0.453	11.51	S-480	1.41	35.7	.363	9.2	6.9	1.2	.82	21	5.6	25	.59	14.9	0.045	1.1	13.0	SST	CG	N
0.453	11.51	S-386	1.44	36.5	.369	9.4	6.8	1.2	.87	22	5.9	26	.43	10.9	0.042	1.1	10.3	SST	CG	N
0.453	11.51	B1-58	1.47	37.3	.375	9.5	7.2	1.3	.70	18	5.1	23	.33	8.4	0.039	1.0	8.50	SPR	CG	N
0.453	11.51	10406	1.50	38.1	.419	10.6	.13	.02	1.3	32	.16	.71	.23	5.7	0.017	0.4	12.3	SST	C	N
0.453	11.51	3610	1.50	38.1	.405	10.3	1.1	.19	1.3	33	1.4	6.3	.20	5.2	0.024	0.6	7.50	MW	C	Z
0.453	11.51	10116	1.50	38.1	.403	10.2	1.4	.25	1.3	33	1.9	8.3	.20	5.1	0.025	0.6	7.00	MW	C	BO
0.453	11.51	S-264	1.50	38.1	.395	10.0	1.8	.31	1.2	29	2.1	9.1	.28	7.0	0.029	0.7	8.50	SST	C	N
0.453	11.51	B14-12	1.50	38.1	.379	9.6	5.1	.89	.80	20	4.1	18	.31	8.0	0.037	0.9	8.50	SST	CG	N
0.453	11.51	10879	1.50	38.1	.377	9.6	5.7	1.0	.77	20	4.4	20	.32	8.2	0.038	1.0	8.50	SST	CG	N
0.453	11.51	LL-14	1.50	38.1	.373	9.5	7.5	1.3	.73	19	5.5	24	.36	9.1	0.040	1.0	9.00	SPR	CG	GI
0.453	11.51	10018	1.50	38.1	.363	9.2	12	2.0	.67	17	7.7	34	.47	12.0	0.045	1.1	9.50	SPR	C	Z
0.453	11.51	K-11	1.50	38.1	.363	9.2	12	2.1	.65	16	7.7	34	.42	10.6	0.045	1.1	9.25	SPR	CG	N
0.453	11.51	11346	1.50	38.1	.363	9.2	11	1.9	.68	17	7.2	32	.42	10.6	0.045	1.1	9.25	SST	CG	N
0.453	11.51	Z-64	1.50	38.1	.349	8.9	18	3.2	.61	15	11	49	.62	15.8	0.052	1.3	11.0	SPR	C	GI
0.453	11.51	B14-39	1.50	38.1	.347	8.8	18	3.2	.59	15	11	49	.56	14.1	0.053	1.3	10.5	SST	CG	N
0.453	11.51	10144	1.50	38.1	.343	8.7	24	4.2	.55	14	13	58	.59	15.0	0.055	1.4	10.8	SPR	CG	Z
0.453	11.51	S-875	1.50	38.1	.343	8.7	22	3.8	.56	14	12	54	.57	14.4	0.055	1.4	10.3	SST	CG	N
0.453	11.51	B1-37	1.53	38.9	.367	9.3	10	1.8	.68	17	6.8	30	.44	11.1	0.043	1.1	9.00	SPR	C	N
0.453	11.51	S-1349	1.56	39.7	.407	10.3	.52	.09	1.3	34	.68	3.0	.24	6.1	0.023	0.6	10.5	SST	CG	N
0.453	11.51	K-51	1.63	41.3	.345	8.8	20	3.5	.61	15	12	55	.62	15.8	0.054	1.4	11.5	SPR	CG	N
0.453	11.51	3775	1.69	42.8	.329	8.4	42	7.3	.44	11	18	82	.71	18.1	0.062	1.6	10.5	HD	C	Z
0.453	11.51	12241	1.69	42.8	.329	8.4	39	6.9	.47	12	18	82	.74	18.9	0.062	1.6	11.0	SPR	C	Z
0.453	11.51	S-97	1.69	42.8	.293	7.4	126	22	.27	6.9	34	153	.88	22.4	0.080	2.0	10.0	SST	C	N
0.453	11.51	B-61	1.75	44.5	.329	8.4	32	5.7	.57	15	18	82	.87	22.0	0.062	1.6	13.0	HD	C	Z
0.453	11.51	S-67	1.78	45.2	.369	9.4	8.2	1.4	.72	18	5.9	26	.42	10.7	0.042	1.1	9.00	SST	C	N
0.453	11.51	S-1486	1.81	46.0	.363	9.2	6.3	1.1	1.2	29	7.2	32	.63	16.0	0.045	1.1	14.0	SST	CG	N
0.453	11.51	10922	1.81	46.0	.309	7.8	50	8.7	.54	14	27	120	1.15	29.3	0.072	1.8	16.0	SPR	CG	Z
0.453	11.51	S-811	1.88	47.6	.385	9.8	2.2	.38	1.5	37	3.1	14	.43	10.8	0.034	0.9	12.5	SST	CG	N
0.453	11.51	11887	1.88	47.6	.355	9.0	12	2.1	.83	21	9.9	44	.66	16.8	0.049	1.2	12.5	SPR	C	N
0.453	11.51	B17-169	1.88	47.6	.329	8.4	25	4.4	.73	18	18	82	.99	25.2	0.062	1.6	16.0	SPR	CG	Z
0.453	11.51	B-25	1.94	49.2	.379	9.6	3.7	.66	1.2	29	4.3	19	.44	11.3	0.037	0.9	12.0	HD	CG	N
0.453	11.51	HH-75	1.94	49.2	.373	9.5	3.9	.68	1.3	33	5.1	23	.62	15.7	0.040	1.0	15.5	SPR	CG	GI
0.453	11.51	11743	2.00	50.8	.345	8.8	13	2.2	.96	24	12	55	.86	21.9	0.054	1.4	15.0	SPR	O	Z
0.453	11.51	10330	2.13	54.0	.345	8.8	14	2.5	.88	22	12	55	.91	23.0	0.054	1.4	15.8	SPR	C	Z
0.453	11.51	3798	2.25	57.2	.269	6.8	219	38	.24	6.1	52	232	1.10	28.0	0.092	2.3	12.0	SPR	CG	Z
0.453	11.51	Z-28	2.34	59.5	.375	9.5	3.6	.63	1.4	36	5.1	23	.59	14.9	0.039	1.0	15.0	SPR	CG	Z
0.453	11.51	11538	2.47	62.7	.353	9.0	11	1.9	.90	23	9.8	44	.78	19.7	0.050	1.3	14.5	SPR	CG	Z
0.453	11.51	12377	2.50	63.5	.357	9.1	7.9	1.4	1.2	30	9.4	42	.84	21.3	0.048	1.2	16.5	SPR	C	Z
0.453	11.51	V-58	2.50	63.5	.355	9.0	11	2.0	.89	23	9.9	44	.65	16.5	0.049	1.2	13.3	SPR	CG	Z
0.453	11.51	4107	2.50	63.5	.353	9.0	9.8	1.7	1.0	26	9.8	44	.85	21.6	0.050	1.3	16.0	SPR	C	Z
0.453	11.51	2878	2.50	63.5	.289	7.3	85	15	.46	12	39	175	1.39	35.4	0.082	2.1	17.0	SPR	CG	Z
0.453	11.51	3684	2.53	64.3	.265	6.7	125	22	.44	11	56	247	2.01	50.9	0.094	2.4	21.0	SPR	CG	GI
0.453	11.51	W-40	2.63	66.7	.359	9.1	5.1	.89	1.6	41	8.2	37	.94	23.9	0.047	1.2	20.0	SST	CG	N
0.453	11.51	11990	2.72	69.0	.373	9.5	3.1	.54	1.8	45	5.5	24	.76	19.3	0.040	1.0	19.0	SPR	CG	GI
0.453	11.51	11817	2.75	69.9	.363	9.2	4.6	.80	1.7	43	7.7	34	.95	24.0	0.045	1.1	21.0	SPR	CG	Z
0.453	11.51	S-414	2.75	69.9	.359	9.1	4.8	.84	1.7	44	8.2	37	.99	25.1	0.047	1.2	21.0	SST	CG	N
0.453	11.51	1731	3.00	76.2	.293	7.4	63	11	.81	21	51	228	1.60	40.6	0.080	2.0	20.0	MW	CG	Z
0.453	11.51	11676	3.50	88.9	.335	8.5	17	2.9	.95	24	16	71	1.18	30.0	0.059	1.5	19.0	SPR	C	Z
0.453	11.51	4172	5.00	127.0	.285	7.2	38	6.7	1.1	28	42	187	3.36	85.3	0.084	2.1	39.0	SPR	C	Z
0.455	11.56	71445	.50	12.7	.377	9.6	23	4.0	.31	7.8	7.0	31	.16	4.0	0.039	1.0	4.00	MW	CG	N
0.455	11.56	71445S	.																	



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.455	11.56	71458	.88	22.4	.363	9.2	21	3.8	.53	13	11	51	.29	7.4	0.046	1.2	6.38	MW	CG	N
0.455	11.56	71458S	.88	22.4	.363	9.2	18	3.2	.42	11	7.7	34	.29	7.4	0.046	1.2	6.38	SST	CG	N
0.455	11.56	71449	1.00	25.4	.377	9.6	11	1.8	.66	17	7.0	31	.25	6.3	0.039	1.0	6.38	MW	CG	N
0.455	11.56	71449S	1.00	25.4	.377	9.6	9.0	1.6	.53	13	4.7	21	.25	6.3	0.039	1.0	6.38	SST	CG	N
0.455	11.56	71459	1.00	25.4	.363	9.2	19	3.3	.61	16	11	51	.32	8.2	0.046	1.2	7.00	MW	CG	N
0.455	11.56	71459S	1.00	25.4	.363	9.2	16	2.8	.49	12	7.7	34	.32	8.2	0.046	1.2	7.00	SST	CG	N
0.455	11.56	71450	1.25	31.8	.377	9.6	8.2	1.4	.85	22	7.0	31	.30	7.6	0.039	1.0	7.63	MW	CG	N
0.455	11.56	71450S	1.25	31.8	.377	9.6	7.0	1.2	.68	17	4.7	21	.30	7.6	0.039	1.0	7.63	SST	CG	N
0.455	11.56	71460	1.25	31.8	.363	9.2	15	2.5	.78	20	11	51	.39	9.9	0.046	1.2	8.50	MW	CG	N
0.455	11.56	71460S	1.25	31.8	.363	9.2	12	2.2	.62	16	7.7	34	.39	9.9	0.046	1.2	8.50	SST	CG	N
0.455	11.56	71451	1.50	38.1	.377	9.6	6.8	1.2	1.0	26	7.0	31	.35	8.8	0.039	1.0	8.88	MW	CG	N
0.455	11.56	71451S	1.50	38.1	.377	9.6	5.7	1.0	.82	21	4.7	21	.35	8.8	0.039	1.0	8.88	SST	CG	N
0.455	11.56	71461	1.50	38.1	.363	9.2	12	2.1	.95	24	11	51	.45	11.5	0.046	1.2	9.88	MW	CG	N
0.455	11.56	71461S	1.50	38.1	.363	9.2	10	1.8	.76	19	7.7	34	.45	11.5	0.046	1.2	9.88	SST	CG	N
0.455	11.56	71452	1.75	44.5	.377	9.6	5.8	1.0	1.2	31	7.0	31	.39	9.9	0.039	1.0	10.0	MW	CG	N
0.455	11.56	71452S	1.75	44.5	.377	9.6	4.9	.86	.97	25	4.7	21	.39	9.9	0.039	1.0	10.0	SST	CG	N
0.455	11.56	71462	1.75	44.5	.363	9.2	10	1.8	1.1	28	11	51	.52	13.1	0.046	1.2	11.3	MW	CG	N
0.455	11.56	71462S	1.75	44.5	.363	9.2	8.7	1.5	.89	22	7.7	34	.52	13.1	0.046	1.2	11.3	SST	CG	N
0.455	11.56	71454	2.00	50.8	.377	9.6	5.5	.96	1.3	32	7.0	31	.40	10.3	0.039	1.0	10.4	MW	CG	N
0.455	11.56	71454S	2.00	50.8	.377	9.6	4.7	.82	1.0	26	4.7	21	.40	10.3	0.039	1.0	10.4	SST	CG	N
0.455	11.56	71464	2.00	50.8	.363	9.2	9.5	1.7	1.2	30	11	51	.55	13.9	0.046	1.2	11.9	MW	CG	N
0.455	11.56	71464S	2.00	50.8	.363	9.2	8.1	1.4	.95	24	7.7	34	.55	13.9	0.046	1.2	11.9	SST	CG	N
0.468	11.89	S-864	.25	6.4	.378	9.6	69	12	.10	2.6	7.0	31	.14	3.4	0.045	1.1	3.00	SST	CG	N
0.468	11.89	DD-28	.31	7.9	.288	7.3	1549	271	.03	.73	44	197	.27	6.9	0.090	2.3	3.00	SST	CG	N
0.468	11.89	A10-53	.34	8.7	.436	11.1	.45	.08	.26	6.7	.12	.53	.08	2.0	0.016	0.4	4.00	SST	C	N
0.468	11.89	PP-57	.44	11.1	.388	9.9	17	2.9	.26	6.6	4.3	19	.18	4.6	0.040	1.0	4.50	SST	CG	N
0.468	11.89	I-99	.44	11.1	.356	9.0	202	35	.07	1.7	13	59	.17	4.3	0.056	1.4	3.00	SPR	CG	Z
0.468	11.89	S-1409	.50	12.7	.410	10.4	6.0	1.0	.33	8.5	2.0	8.9	.11	2.8	0.029	0.7	3.75	SST	CG	N
0.468	11.89	G-42	.50	12.7	.348	8.8	159	28	.10	2.4	15	68	.21	5.3	0.060	1.5	3.50	SST	CG	N
0.468	11.89	MM-87	.50	12.7	.344	8.7	106	19	.17	4.3	18	80	.31	7.9	0.062	1.6	5.00	HD	CG	N
0.468	11.89	00-51	.53	13.5	.408	10.4	2.5	.43	.32	8.2	.79	3.5	.21	5.3	0.030	0.8	7.00	SST	CG	N
0.468	11.89	S-35	.53	13.5	.392	10.0	13	2.3	.32	8.1	4.3	19	.21	5.3	0.038	1.0	4.50	SST	C	N
0.468	11.89	3638	.53	13.5	.344	8.7	127	22	.20	5.0	25	111	.28	7.1	0.062	1.6	4.50	MW	CG	Z
0.468	11.89	3800	.56	14.3	.384	9.8	39	6.8	.16	4.0	6.1	27	.19	4.8	0.042	1.1	3.50	SPR	C	Z
0.468	11.89	B17-148	.59	15.1	.400	10.2	12	2.1	.29	7.4	3.4	15	.14	3.5	0.034	0.9	4.00	SPR	CG	Z
0.468	11.89	S-812	.59	15.1	.398	10.1	5.9	1.0	.35	8.8	2.1	9.1	.25	6.2	0.035	0.9	6.00	SST	C	N
0.468	11.89	S-3130	.63	15.9	.422	10.7	1.3	.23	.49	12	.64	2.9	.14	3.5	0.023	0.6	5.00	SST	C	N
0.468	11.89	S-3006	.63	15.9	.420	10.7	1.6	.28	.48	12	.76	3.4	.14	3.7	0.024	0.6	5.00	SST	C	N
0.468	11.89	A15-37	.63	15.9	.414	10.5	4.5	.79	.36	9.1	1.6	7.2	.13	3.3	0.027	0.7	3.75	SST	C	N
0.468	11.89	I-7	.63	15.9	.398	10.1	9.2	1.6	.36	9.2	3.3	15	.19	4.9	0.035	0.9	4.50	SST	C	N
0.468	11.89	A10-40	.69	17.4	.410	10.4	3.3	.57	.51	13	1.7	7.4	.18	4.6	0.029	0.7	5.25	SST	C	N
0.468	11.89	3877	.69	17.4	.400	10.2	7.8	1.4	.44	11	3.4	15	.20	5.2	0.034	0.9	5.00	SPR	C	Z
0.468	11.89	L-41	.69	17.4	.382	9.7	21	3.7	.31	7.8	6.6	29	.22	5.5	0.043	1.1	5.00	SPR	CG	Z
0.468	11.89	I-91	.72	18.2	.392	10.0	6.1	1.1	.43	11	2.6	12	.29	7.2	0.038	1.0	7.50	SST	CG	N
0.468	11.89	S-451	.72	18.2	.358	9.1	47	8.3	.25	6.4	12	53	.30	7.7	0.055	1.4	5.50	SST	CG	N
0.468	11.89	S-1091	.72	18.2	.340	8.6	71	12	.26	6.7	19	82	.42	10.6	0.064	1.6	6.50	SST	CG	N
0.468	11.89	K-32	.75	19.1	.408	10.4	4.0	.69	.56	14	2.2	9.8	.20	5.0	0.030	0.8	5.50	MW	C	Z
0.468	11.89	B14-70	.75	19.1	.390	9.9	12	2.1	.41	10	4.9	22	.21	5.4	0.039	1.0	5.50	SPR	CG	Z
0.468	11.89	CC-55	.75	19.1	.384	9.8	13	2.2	.46	12	5.7	25	.25	6.4	0.042	1.1	6.00	SST	CG	N
0.468	11.89	3203	.78	19.8	.416	10.6	2.8	.48	.63	16	1.7	7.8	.15	3.8	0.026	0.7	4.75	MW	C	Z
0.468	11.89	MM-100	.78	19.8	.348	8.8	57	10	.27	6.8	15	68	.38	9.5	0.060	1.5	6.25	SST	CG	N
0.468	11.89	10800	.81	20.6	.422	10.7	.68	.12	.61	15	.41	1.8	.21	5.3	0.023	0.6	8.00	SST	C	N
0.468	11.89	A11-65	.81	20.6	.420	10.7	.94	.17	.62	16	.58	2.6	.20	5.0	0.024	0.6	7.00	SST	C	N
0.468	11.89	CC-86	.81	20.6	.416	10.6	1.8	.31	.64	16	1.1	5.0	.18	4.5	0.026	0.7	5.75	SST	C	N
0.468	11.89	S-50	.81	20.6	.408	10.4	3.0	.53	.63	16	1.9	8.5	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.468	11.89	O-47	.81	20.6	.384	9.8	7.2	1.3	.39	10	2.8	13	.42	10.7	0.042	1.1	10.0	SPR	CG	BO
0.468	11.89	A15-33	.81	20.6	.374	9.5	21	3.7	.38	9.7	8.0	36	.28	7.2	0.047	1.2	6.00	SST	CG	N
0.468	11.89	1613	.83	21.0	.416	10.6	2.5	.44	.67	17	1.7	7.6	.16	4.0	0.026	0.7	5.00	MW	C	Z
0.468	11.89	S-473	.83	21.0	.406	10.3	3.1	.54	.60	15	1.8	8.1	.23	5.9	0.031	0.8	6.50	SST	C	N
0.468	11.89	3643	.83	21.0	.384	9.8	12	2.1	.50	13	6.1	27	.28	7.2	0.042	1.1	6.75	HD	CG	GI
0.468	11.89	A14-15	.84	21.4	.396	10.1	4.6	.81	.53	13	2.4	11	.32	8.0	0.036	0.9	7.75	SST	C	N
0.468	11.89	3257	.88	22.2	.412	10.5	3.0	.52	.69	18	2.1	9.1	.18	4.6	0.028	0.7	5.50	MW	C	Z
0.468	11.89	A-75	.88	22.2	.356	9.0	29	5.1	.43	11	13	56	.45	11.4	0.056	1.4	8.00	SST	CG	N
0.468	11.89	K-84	.88	22.2	.348	8.8	68	12	.22	5.7	15	68	.39	9.9	0.060	1.5	5.50	SST	C	N
0.468	11.89	B14-8	.88	22.2	.310	7.9	200	35	.17	4.4	34	153	.53	13.5	0.079	2.0	6.75	SPR	CG	Z
0.468	11.89	11201	.91	23.0	.408	10.4	2.7	.48	.68	17	1.9	8.3	.23	5.7	0.030	0.8	6.50	SST	C	N
0.468	11.89	12105	.91	23.0	.360	9.1	29	5.0	.42	11	12	53	.43	11.0	0.054	1.4	8.00	SPR	CG	N
0.468	11.89	I-54	.94	23.8	.406	10.3	3.2	.56	.72	18	2.3	10	.22	5.5	0.031	0.8	7.00	MW	CG	Z
0.468	11.89	J-60-A	.94	23.8	.404	10.3	4.5	.80	.71	18</										



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.468	11.89	S-1344	1.00	25.4	.386	9.8	10	1.8	.53	13	5.3	24	.31	7.8	0.041	1.0	6.50	SST	C	N
0.468	11.89	3504	1.00	25.4	.358	9.1	34	5.9	.37	9.5	13	56	.41	10.5	0.055	1.4	7.50	SPR	CG	Z
0.468	11.89	S-3079	1.00	25.4	.344	8.7	46	8.1	.37	9.3	17	75	.56	14.2	0.062	1.6	8.00	SST	C	N
0.468	11.89	3708	1.00	25.4	.338	8.6	71	12	.29	7.3	21	92	.49	12.4	0.065	1.7	7.50	SPR	CG	Z
0.468	11.89	PP-20	1.00	25.4	.328	8.3	100	17	.24	6.2	24	108	.53	13.3	0.070	1.8	7.50	SPR	CG	Z
0.468	11.89	10780	1.03	26.2	.398	10.1	2.6	.46	.65	16	1.7	7.5	.39	9.8	0.035	0.9	11.0	SST	CG	N
0.468	11.89	NN-51	1.03	26.2	.368	9.3	18	3.1	.54	14	9.6	42	.45	11.4	0.050	1.3	9.00	SPR	CG	Z
0.468	11.89	A11-12	1.06	27.0	.408	10.4	2.5	.43	.85	22	2.1	9.3	.21	5.3	0.030	0.8	7.00	SST	CG	N
0.468	11.89	EE-92	1.06	27.0	.374	9.5	21	3.7	.41	10	8.5	38	.31	7.8	0.047	1.2	6.50	SPR	CG	Z
0.468	11.89	10641	1.06	27.0	.344	8.7	71	12	.25	6.5	18	80	.40	10.2	0.062	1.6	6.50	SPR	CG	N
0.468	11.89	3962	1.06	27.0	.258	6.6	552	97	.12	3.1	68	304	.81	20.7	0.105	2.7	7.75	SST	CG	N
0.468	11.89	A10-29	1.09	27.8	.398	10.1	3.1	.55	.76	19	2.4	11	.33	8.4	0.035	0.9	9.50	SST	CG	N
0.468	11.89	2981	1.09	27.8	.324	8.2	89	16	.30	7.5	26	117	.65	16.5	0.072	1.8	9.00	SPR	CG	Z
0.468	11.89	10421	1.11	28.2	.296	7.5	217	38	.20	5.1	44	195	.73	18.6	0.086	2.2	8.50	SPR	CG	Z
0.468	11.89	Z-44	1.13	28.6	.398	10.1	6.6	1.2	.54	14	3.6	16	.25	6.2	0.035	0.9	6.00	SPR	C	Z
0.468	11.89	S-488	1.13	28.6	.394	10.0	5.9	1.0	.67	17	3.9	18	.30	7.5	0.037	0.9	7.00	SST	C	N
0.468	11.89	HH-88	1.13	28.6	.378	9.6	9.7	1.7	.63	16	6.1	27	.50	12.6	0.045	1.1	10.0	SPR	C	Z
0.468	11.89	AA-78	1.13	28.6	.368	9.3	15	2.7	.58	15	8.8	39	.55	14.0	0.050	1.3	10.0	SPR	C	Z
0.468	11.89	3591	1.13	28.6	.348	8.8	46	8.0	.49	13	23	101	.48	12.2	0.060	1.5	8.00	MW	CG	Z
0.468	11.89	S-1341	1.13	28.6	.324	8.2	77	14	.32	8.1	25	110	.65	16.5	0.072	1.8	9.00	SST	CG	N
0.468	11.89	B3-33	1.16	29.4	.408	10.4	2.3	.40	.89	23	2.0	9.1	.27	6.9	0.030	0.8	8.00	MW	C	N
0.468	11.89	11770	1.16	29.4	.404	10.3	2.3	.40	.84	21	1.9	8.5	.32	8.1	0.032	0.8	10.0	SPR	CG	Z
0.468	11.89	Y-56	1.16	29.4	.338	8.6	52	9.2	.37	9.4	19	86	.55	14.0	0.065	1.7	8.50	SST	CG	N
0.468	11.89	11376	1.19	30.2	.374	9.5	19	3.2	.43	11	8.0	36	.31	7.8	0.047	1.2	6.50	SST	CG	N
0.468	11.89	QQ-65	1.19	30.2	.352	8.9	30	5.2	.50	13	15	66	.58	14.7	0.058	1.5	10.0	SPR	CG	Z
0.468	11.89	2720	1.19	30.2	.282	7.2	340	60	.22	5.5	73	326	.74	18.9	0.093	2.4	8.00	MW	CG	Z
0.468	11.89	10470	1.19	30.2	.264	6.7	508	89	.13	3.4	68	302	.84	21.4	0.102	2.6	8.25	SPR	CG	Z
0.468	11.89	A-25	1.22	31.0	.368	9.3	14	2.5	.66	17	9.6	42	.53	13.3	0.050	1.3	10.5	SPR	CG	N
0.468	11.89	N-56	1.22	31.0	.362	9.2	21	3.7	.54	14	11	50	.50	12.8	0.053	1.3	9.50	SPR	CG	Z
0.468	11.89	M-111	1.22	31.0	.360	9.1	23	4.0	.52	13	12	53	.51	13.0	0.054	1.4	9.50	SPR	CG	Z
0.468	11.89	Z-50	1.25	31.8	.436	11.1	.06	.01	.92	23	.05	24	.33	8.3	0.016	0.4	19.5	MW	C	Z
0.468	11.89	10097	1.25	31.8	.398	10.1	6.6	1.2	.54	14	3.6	16	.25	6.2	0.035	0.9	6.00	SPR	C	Z
0.468	11.89	L-42	1.25	31.8	.386	9.8	5.0	.87	.74	19	3.7	16	.51	13.0	0.041	1.0	12.5	MW	CG	Z
0.468	11.89	F-55	1.25	31.8	.378	9.6	9.7	1.7	.77	20	7.5	33	.45	11.4	0.045	1.1	10.0	SPR	CG	GI
0.468	11.89	TT-54	1.25	31.8	.378	9.6	8.2	1.4	.69	17	5.6	25	.56	14.3	0.045	1.1	11.5	SPR	C	Z
0.468	11.89	KK-77	1.25	31.8	.378	9.6	11	1.9	.65	16	7.0	31	.37	9.4	0.045	1.1	8.25	SST	CG	N
0.468	11.89	RR-67	1.25	31.8	.370	9.4	11	1.9	.71	18	7.7	34	.54	13.7	0.049	1.2	11.0	SST	CG	N
0.468	11.89	S-1697	1.25	31.8	.368	9.3	15	2.7	.59	15	9.0	40	.45	11.4	0.050	1.3	9.00	SST	CG	N
0.468	11.89	3086	1.25	31.8	.344	8.7	45	7.9	.40	10	18	80	.56	14.2	0.062	1.6	9.00	SPR	CG	Z
0.468	11.89	10555	1.25	31.8	.292	7.4	180	31	.26	6.6	47	208	.95	24.0	0.088	2.2	10.8	SPR	CG	Z
0.468	11.89	S-1167	1.28	32.5	.394	10.0	6.9	1.2	.57	15	3.9	18	.27	6.8	0.037	0.9	6.25	SST	C	N
0.468	11.89	10696	1.31	33.3	.386	9.8	6.7	1.2	.85	22	5.7	25	.40	10.2	0.041	1.0	9.75	SPR	CG	Z
0.468	11.89	A13-65	1.31	33.3	.372	9.4	10	1.7	.72	18	7.2	32	.59	15.0	0.048	1.2	12.3	SPR	CG	N
0.468	11.89	B8-57	1.31	33.3	.288	7.3	249	44	.19	4.9	48	213	.81	20.6	0.090	2.3	9.00	SPR	CG	Z
0.468	11.89	12470	1.31	33.3	.284	7.2	323	57	.16	4.0	51	226	.74	18.7	0.092	2.3	8.00	SPR	CG	Z
0.468	11.89	3966	1.38	34.9	.414	10.5	1.3	.23	1.1	29	1.5	6.7	.24	6.0	0.027	0.7	8.75	MW	CG	Z
0.468	11.89	10855	1.38	34.9	.408	10.4	1.9	.33	1.1	28	2.1	9.2	.29	7.2	0.030	0.8	8.50	SST	C	N
0.468	11.89	S-1447	1.38	34.9	.392	10.0	5.7	1.0	.75	19	4.3	19	.29	7.5	0.038	1.0	7.75	SST	CG	N
0.468	11.89	CC-48	1.38	34.9	.384	9.8	6.3	1.1	.91	23	5.7	25	.46	11.7	0.042	1.1	10.0	SST	C	N
0.468	11.89	S-181	1.38	34.9	.380	9.7	9.8	1.7	.67	17	6.6	29	.36	9.2	0.044	1.1	8.25	SST	CG	N
0.468	11.89	S-214	1.38	34.9	.378	9.6	7.5	1.3	.84	21	6.3	28	.54	13.7	0.045	1.1	11.0	SST	C	N
0.468	11.89	S-3063	1.38	34.9	.324	8.2	60	11	.41	10	25	110	.79	20.1	0.072	1.8	11.0	SST	CG	N
0.468	11.89	FF-77	1.38	34.9	.288	7.3	217	38	.20	5.2	44	197	.81	20.6	0.090	2.3	9.00	SST	CG	N
0.468	11.89	12426	1.41	35.7	.412	10.5	1.2	.21	1.1	28	1.4	6.1	.29	7.5	0.028	0.7	9.50	SST	C	N
0.468	11.89	DD-82	1.41	35.7	.328	8.3	54	9.4	.42	11	23	101	.77	19.6	0.070	1.8	11.0	SST	CG	N
0.468	11.89	3737	1.44	36.5	.400	10.2	3.9	.69	.88	22	3.4	15	.31	7.8	0.034	0.9	8.00	SPR	C	Z
0.468	11.89	HH-92	1.44	36.5	.376	9.6	8.3	1.4	.91	23	7.5	33	.51	12.9	0.046	1.2	11.0	SST	CG	N
0.468	11.89	12494	1.44	36.5	.372	9.4	8.2	1.4	.69	18	5.7	25	.74	18.9	0.048	1.2	14.5	SPR	C	N
0.468																				



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.468	11.89	A15-61	1.94	49.2	.376	9.6	8.7	1.5	.86	22	7.5	33	.49	12.6	0.046	1.2	10.8	SST	CG	N
0.468	11.89	RR-62	2.00	50.8	.418	10.6	.51	.09	1.7	42	.84	3.7	.35	8.9	0.025	0.6	13.0	SST	C	N
0.468	11.89	S-1404	2.00	50.8	.378	9.6	5.1	.90	1.3	32	6.5	29	.73	18.6	0.045	1.1	15.3	SST	C	N
0.468	11.89	3573	2.00	50.8	.372	9.4	9.4	1.6	1.3	34	13	56	.62	15.8	0.048	1.2	13.0	MW	CG	Z
0.468	11.89	KK-34	2.00	50.8	.348	8.8	20	3.6	.76	19	15	68	.84	21.3	0.060	1.5	14.0	SST	CG	N
0.468	11.89	2852	2.00	50.8	.340	8.6	37	6.4	.75	19	27	121	.77	19.5	0.064	1.6	12.0	MW	CG	Z
0.468	11.89	10923	2.06	52.4	.334	8.5	45	7.9	.50	13	22	100	.87	22.1	0.067	1.7	12.0	SPR	C	Z
0.468	11.89	4300	2.13	54.0	.360	9.1	13	2.2	.94	24	12	53	.89	22.6	0.054	1.4	15.5	SPR	C	Z
0.468	11.89	S-1104	2.13	54.0	.268	6.8	201	35	.30	7.5	60	265	1.45	36.8	0.100	2.5	14.5	SST	CG	N
0.468	11.89	3225	2.34	59.5	.308	7.8	64	11	.55	14	36	158	1.41	35.9	0.080	2.0	17.8	SPR	CG	Z
0.468	11.89	A13-32	2.41	61.1	.304	7.7	68	12	.56	14	38	170	1.52	38.5	0.082	2.1	18.5	SPR	CG	N
0.468	11.89	10062	2.50	63.5	.388	9.9	3.2	.57	1.6	42	5.3	24	.66	16.8	0.040	1.0	16.5	SPR	CG	Z
0.468	11.89	12	2.50	63.5	.360	9.1	11	1.9	1.1	29	12	53	1.04	26.4	0.054	1.4	18.3	HD	C	Z
0.468	11.89	3693	2.50	63.5	.342	8.7	24	4.3	.77	20	19	84	1.07	27.2	0.063	1.6	16.0	SPR	C	Z
0.468	11.89	S-1536	2.56	65.1	.360	9.1	7.5	1.3	1.4	35	10	46	1.19	30.2	0.054	1.4	22.0	SST	CG	N
0.468	11.89	NN-91	2.63	66.7	.396	10.1	2.0	.35	1.8	46	3.6	16	.58	14.6	0.036	0.9	15.0	SST	C	N
0.468	11.89	S-1153	2.63	66.7	.388	9.9	2.4	.42	1.8	46	4.4	19	.80	20.3	0.040	1.0	19.0	SST	C	N
0.468	11.89	3014	2.88	73.0	.318	8.1	37	6.6	.79	20	30	132	1.65	41.9	0.075	1.9	22.0	SPR	CG	Z
0.468	11.89	S-496	3.06	77.8	.374	9.5	3.8	.67	2.0	50	7.4	33	1.10	28.1	0.047	1.2	23.5	SST	CG	N
0.468	11.89	2818	3.06	77.8	.338	8.6	25	4.3	.84	21	21	92	1.24	31.4	0.065	1.7	18.0	SPR	C	Z
0.468	11.89	4210	3.50	88.9	.366	9.3	8.3	1.4	1.2	31	10	45	.98	24.9	0.051	1.3	18.3	SPR	C	Z
0.468	11.89	11522	3.50	88.9	.344	8.7	17	2.9	1.1	27	18	80	1.36	34.6	0.062	1.6	21.0	SPR	CG	GI
0.468	11.89	11893	3.50	88.9	.326	8.3	30	5.2	.80	20	24	105	1.38	35.2	0.071	1.8	19.5	SST	CG	N
0.468	11.89	S-242	3.50	88.9	.308	7.8	33	5.8	1.0	26	33	148	2.28	57.9	0.080	2.0	28.5	SST	CG	N
0.468	11.89	3032	4.00	101.6	.258	6.6	126	22	.58	15	74	328	3.26	82.7	0.105	2.7	31.0	SPR	CG	Z
0.468	11.89	11822	4.94	125.4	.360	9.1	4.9	.86	2.4	62	12	53	2.05	52.1	0.054	1.4	37.0	SPR	C	Z
0.468	11.89	1571	8.00	203.2	.348	8.8	6.2	1.1	2.6	67	16	72	2.85	72.4	0.060	1.5	46.5	SPR	C	Z
0.468	11.89	12243	10.3	260.4	.360	9.1	2.3	.40	5.2	132	12	53	4.16	105.6	0.054	1.4	77.0	SPR	CG	Z
0.480	12.19	71465	.50	12.7	.410	10.4	16	2.7	.31	7.8	4.8	21	.12	3.1	0.035	0.9	3.50	MW	CG	N
0.480	12.19	71465S	.50	12.7	.410	10.4	13	2.3	.24	6.2	3.3	15	.12	3.1	0.035	0.9	3.50	SST	CG	N
0.480	12.19	71476	.50	12.7	.404	10.3	20	3.5	.31	7.8	6.2	27	.14	3.6	0.038	1.0	3.75	MW	CG	N
0.480	12.19	71476S	.50	12.7	.404	10.3	17	3.0	.24	6.2	4.2	19	.14	3.6	0.038	1.0	3.75	SST	CG	N
0.480	12.19	71490	.50	12.7	.396	10.1	28	4.9	.30	7.5	8.3	37	.16	4.1	0.042	1.1	3.88	MW	CG	N
0.480	12.19	71490S	.50	12.7	.396	10.1	24	4.2	.24	6.0	5.6	25	.16	4.1	0.042	1.1	3.88	SST	CG	N
0.480	12.19	71504	.50	12.7	.390	9.9	35	6.1	.29	7.4	10	45	.18	4.6	0.045	1.1	4.00	MW	CG	N
0.480	12.19	71504S	.50	12.7	.390	9.9	30	5.2	.23	5.9	6.9	31	.18	4.6	0.045	1.1	4.00	SST	CG	N
0.480	12.19	71518	.50	12.7	.378	9.6	59	10	.23	5.9	14	61	.21	5.3	0.051	1.3	4.13	MW	CG	N
0.480	12.19	71518S	.50	12.7	.378	9.6	50	8.8	.18	4.7	9.3	41	.21	5.3	0.051	1.3	4.13	SST	CG	N
0.480	12.19	71532	.50	12.7	.370	9.4	72	13	.24	6.0	17	76	.24	6.1	0.055	1.4	4.38	MW	CG	N
0.480	12.19	71532S	.50	12.7	.370	9.4	61	11	.19	4.8	12	52	.24	6.1	0.055	1.4	4.38	SST	CG	N
0.480	12.19	71546	.50	12.7	.362	9.2	103	18	.21	5.2	21	94	.25	6.4	0.059	1.5	4.25	MW	CG	N
0.480	12.19	71546S	.50	12.7	.362	9.2	87	15	.16	4.2	14	63	.25	6.4	0.059	1.5	4.25	SST	CG	N
0.480	12.19	71560	.50	12.7	.354	9.0	123	21	.21	5.3	25	113	.28	7.2	0.063	1.6	4.50	MW	CG	N
0.480	12.19	71560S	.50	12.7	.354	9.0	104	18	.17	4.2	17	77	.28	7.2	0.063	1.6	4.50	SST	CG	N
0.480	12.19	71575	.50	12.7	.346	8.8	180	31	.17	4.3	30	136	.28	7.2	0.067	1.7	4.25	MW	CG	N
0.480	12.19	71575S	.50	12.7	.346	8.8	153	27	.14	3.4	21	92	.28	7.2	0.067	1.7	4.25	SST	CG	N
0.480	12.19	71588	.50	12.7	.336	8.5	256	45	.14	3.6	36	160	.31	7.8	0.072	1.8	4.25	MW	CG	N
0.480	12.19	71588S	.50	12.7	.336	8.5	217	38	.11	2.8	24	107	.31	7.8	0.072	1.8	4.25	SST	CG	N
0.480	12.19	71603	.50	12.7	.332	8.4	289	51	.13	3.4	39	173	.31	8.0	0.074	1.9	4.25	MW	CG	N
0.480	12.19	71603S	.50	12.7	.332	8.4	246	43	.11	2.7	26	116	.31	8.0	0.074	1.9	4.25	SST	CG	N
0.480	12.19	71618	.50	12.7	.318	8.1	447	78	.11	2.9	50	224	.33	8.5	0.081	2.1	4.13	MW	CG	N
0.480	12.19	71618S	.50	12.7	.318	8.1	380	66	.09	2.3	34	150	.33	8.5	0.081	2.1	4.13	SST	CG	N
0.480	12.19	71466	.63	16.0	.410	10.4	12	2.1	.40	10	4.8	21	.14	3.6	0.035	0.9	4.00	MW	CG	N
0.480	12.19	71466S	.63	16.0	.410	10.4	10	1.8	.31	8.0	3.3	15	.14	3.6	0.035	0.9	4.00	SST	CG	N
0.480	12.19	71477	.63	16.0	.404	10.3	15	2.6	.41	10	6.2	27	.17	4.2	0.038	1.0	4.38	MW	CG	N
0.480	12.19	71477S	.63	16.0	.404	10.3	13	2.2	.33	8.3	4.2	19	.17	4.2	0.038	1.0	4.38	SST	CG	N
0.480	12.19	71491	.63	16.0	.396	10.1	22	3.8	.38	9.8	8.3	37	.19	4.8	0.042	1.1	4.50	MW	CG	N
0.480	12.19	71491S	.63	16.0	.396	10.1	18	3.2	.31	7.8	5.6	25	.19	4.8	0.042	1.1	4.50	SST	CG	N
0.480	12.19	71505	.63	16.0	.390	9.9	28	4.9	.36	9.2	10	45	.20	5.1	0.045	1.1	4.50	MW	CG	N
0.480	12.19	71505S	.63	16.0	.390	9.9	24	4.2	.29	7.3	6.9	31	.20	5.1	0.045	1.1	4.50	SST	CG	N
0.480	12.19	71519	.63	16.0	.378	9.6	45	7.9	.30	7.7	14	61	.24	6.2	0.051	1.3	4.75	MW	CG	N
0.480	12.19	71519S	.63	16.0	.378	9.6	38	6.7	.24	6.2	9.3	41	.24	6.2	0.051	1.3	4.75	SST	CG	N
0.480	12.19	71533	.63	16.0	.370	9.4	56	9.8	.31	7.8	17	76	.28	7.0	0.055	1.4	5.00	MW	CG	N
0.480	12.19	71533S	.63	16.0	.370	9.4	48	8.3	.24	6.2	12	52	.28	7.0	0.055	1.4	5.00	SST	CG	N
0.480	12.19	71547	.63	16.0	.362	9.2	78	14	.27	6.8	21	94	.30	7.5	0.059	1.5	5.00	MW	CG	N
0.480	12.19	71547S	.63	16.0	.362	9.2	67	12	.21	5.4	14	63	.30	7.5	0.059	1.5	5.00	SST	CG	N
0.480	12.19	71561	.63	16.0	.354	9.0	95	17	.27	6.8	25	113	.33	8.4	0.063	1.6	5.25	MW	CG	N
0.480	12.19	71561S	.63	16.0	.354	9.0	81	14	.21	5.4	17	77	.33	8.4	0.063	1.6	5.25	SST	CG	N



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.480	12.19	71478	.75	19.1	.404	10.3	13	2.2	.49	12	6.2	27	.18	4.6	0.038	1.0	4.75	MW	CG	N
0.480	12.19	71478S	.75	19.1	.404	10.3	11	1.9	.39	9.9	4.2	19	.18	4.6	0.038	1.0	4.75	SST	CG	N
0.480	12.19	71492	.75	19.1	.396	10.1	18	3.2	.46	12	8.3	37	.21	5.3	0.042	1.1	5.00	MW	CG	N
0.480	12.19	71492S	.75	19.1	.396	10.1	15	2.7	.37	9.3	5.6	25	.21	5.3	0.042	1.1	5.00	SST	CG	N
0.480	12.19	71506	.75	19.1	.390	9.9	22	3.9	.46	12	10	45	.24	6.0	0.045	1.1	5.25	MW	CG	N
0.480	12.19	71506S	.75	19.1	.390	9.9	19	3.3	.37	9.3	6.9	31	.24	6.0	0.045	1.1	5.25	SST	CG	N
0.480	12.19	71520	.75	19.1	.378	9.6	37	6.5	.37	9.3	14	61	.27	6.8	0.051	1.3	5.25	MW	CG	N
0.480	12.19	71520S	.75	19.1	.378	9.6	32	5.6	.29	7.4	9.3	41	.27	6.8	0.051	1.3	5.25	SST	CG	N
0.480	12.19	71534	.75	19.1	.370	9.4	47	8.2	.36	9.3	17	76	.31	7.9	0.055	1.4	5.63	MW	CG	N
0.480	12.19	71534S	.75	19.1	.370	9.4	40	7.0	.29	7.4	12	52	.31	7.9	0.055	1.4	5.63	SST	CG	N
0.480	12.19	71548	.75	19.1	.362	9.2	63	11	.33	8.5	21	94	.34	8.6	0.059	1.5	5.75	MW	CG	N
0.480	12.19	71548S	.75	19.1	.362	9.2	53	9.4	.27	6.8	14	63	.34	8.6	0.059	1.5	5.75	SST	CG	N
0.480	12.19	71562	.75	19.1	.354	9.0	78	14	.33	8.4	25	113	.38	9.6	0.063	1.6	6.00	MW	CG	N
0.480	12.19	71562S	.75	19.1	.354	9.0	66	12	.26	6.7	17	77	.38	9.6	0.063	1.6	6.00	SST	CG	N
0.480	12.19	71577	.75	19.1	.346	8.8	107	19	.29	7.3	30	136	.39	10.0	0.067	1.7	5.88	MW	CG	N
0.480	12.19	71577S	.75	19.1	.346	8.8	91	16	.23	5.8	21	92	.39	10.0	0.067	1.7	5.88	SST	CG	N
0.480	12.19	71590	.75	19.1	.336	8.5	150	26	.24	6.1	36	160	.41	10.5	0.072	1.8	5.75	MW	CG	N
0.480	12.19	71590S	.75	19.1	.336	8.5	128	22	.19	4.8	24	107	.41	10.5	0.072	1.8	5.75	SST	CG	N
0.480	12.19	71605	.75	19.1	.332	8.4	169	30	.23	5.8	39	173	.43	10.8	0.074	1.9	5.75	MW	CG	N
0.480	12.19	71605S	.75	19.1	.332	8.4	144	25	.18	4.6	26	116	.43	10.8	0.074	1.9	5.75	SST	CG	N
0.480	12.19	71620	.75	19.1	.318	8.1	257	45	.20	5.0	50	224	.47	11.8	0.081	2.1	5.75	MW	CG	N
0.480	12.19	71620S	.75	19.1	.318	8.1	218	38	.15	3.9	34	150	.47	11.8	0.081	2.1	5.75	SST	CG	N
0.480	12.19	71468	.88	22.4	.410	10.4	8.3	1.5	.58	15	4.8	21	.18	4.4	0.035	0.9	5.00	MW	CG	N
0.480	12.19	71468S	.88	22.4	.410	10.4	7.1	1.2	.46	12	3.3	15	.18	4.4	0.035	0.9	5.00	SST	CG	N
0.480	12.19	71479	.88	22.4	.404	10.3	11	1.8	.59	15	6.2	27	.20	5.1	0.038	1.0	5.25	MW	CG	N
0.480	12.19	71479S	.88	22.4	.404	10.3	8.9	1.6	.47	12	4.2	19	.20	5.1	0.038	1.0	5.25	SST	CG	N
0.480	12.19	71493	.88	22.4	.396	10.1	15	2.6	.55	14	8.3	37	.23	5.9	0.042	1.1	5.50	MW	CG	N
0.480	12.19	71493S	.88	22.4	.396	10.1	13	2.2	.44	11	5.6	25	.23	5.9	0.042	1.1	5.50	SST	CG	N
0.480	12.19	71507	.88	22.4	.390	9.9	19	3.3	.53	14	10	45	.26	6.6	0.045	1.1	5.75	MW	CG	N
0.480	12.19	71507S	.88	22.4	.390	9.9	16	2.8	.42	11	6.9	31	.26	6.6	0.045	1.1	5.75	SST	CG	N
0.480	12.19	71521	.88	22.4	.378	9.6	30	5.3	.45	11	14	61	.31	7.8	0.051	1.3	6.00	MW	CG	N
0.480	12.19	71521S	.88	22.4	.378	9.6	26	4.5	.36	9.1	9.3	41	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.480	12.19	71535	.88	22.4	.370	9.4	38	6.7	.45	11	17	76	.36	9.1	0.055	1.4	6.50	MW	CG	N
0.480	12.19	71535S	.88	22.4	.370	9.4	32	5.7	.36	9.1	12	52	.36	9.1	0.055	1.4	6.50	SST	CG	N
0.480	12.19	71549	.88	22.4	.362	9.2	51	8.9	.41	10	21	94	.39	9.9	0.059	1.5	6.63	MW	CG	N
0.480	12.19	71549S	.88	22.4	.362	9.2	43	7.6	.33	8.4	14	63	.39	9.9	0.059	1.5	6.63	SST	CG	N
0.480	12.19	71563	.88	22.4	.354	9.0	66	11	.39	9.9	25	113	.43	10.8	0.063	1.6	6.75	MW	CG	N
0.480	12.19	71563S	.88	22.4	.354	9.0	56	9.7	.31	7.9	17	77	.43	10.8	0.063	1.6	6.75	SST	CG	N
0.480	12.19	71578	.88	22.4	.346	8.8	88	15	.34	8.8	30	136	.44	11.3	0.067	1.7	6.63	MW	CG	N
0.480	12.19	71578S	.88	22.4	.346	8.8	75	13	.27	7.0	21	92	.44	11.3	0.067	1.7	6.63	SST	CG	N
0.480	12.19	71591	.88	22.4	.336	8.5	124	22	.29	7.4	36	160	.48	12.1	0.072	1.8	6.63	MW	CG	N
0.480	12.19	71591S	.88	22.4	.336	8.5	105	18	.23	5.8	24	107	.48	12.1	0.072	1.8	6.63	SST	CG	N
0.480	12.19	71606	.88	22.4	.332	8.4	139	24	.28	7.1	39	173	.49	12.5	0.074	1.9	6.63	MW	CG	N
0.480	12.19	71606S	.88	22.4	.332	8.4	118	21	.22	5.6	26	116	.49	12.5	0.074	1.9	6.63	SST	CG	N
0.480	12.19	71621	.88	22.4	.318	8.1	210	37	.24	6.1	50	224	.54	13.6	0.081	2.1	6.63	MW	CG	N
0.480	12.19	71621S	.88	22.4	.318	8.1	179	31	.19	4.8	34	150	.54	13.6	0.081	2.1	6.63	SST	CG	N
0.480	12.19	71469	1.00	25.4	.410	10.4	7.2	1.3	.67	17	4.8	21	.19	4.8	0.035	0.9	5.38	MW	CG	N
0.480	12.19	71469S	1.00	25.4	.410	10.4	6.1	1.1	.53	14	3.3	15	.19	4.8	0.035	0.9	5.38	SST	CG	N
0.480	12.19	71480	1.00	25.4	.404	10.3	9.3	1.6	.66	17	6.2	27	.22	5.5	0.038	1.0	5.75	MW	CG	N
0.480	12.19	71480S	1.00	25.4	.404	10.3	7.9	1.4	.53	13	4.2	19	.22	5.5	0.038	1.0	5.75	SST	CG	N
0.480	12.19	71494	1.00	25.4	.396	10.1	13	2.3	.64	16	8.3	37	.26	6.5	0.042	1.1	6.13	MW	CG	N
0.480	12.19	71494S	1.00	25.4	.396	10.1	11	1.9	.51	13	5.6	25	.26	6.5	0.042	1.1	6.13	SST	CG	N
0.480	12.19	71508	1.00	25.4	.390	9.9	17	3.0	.60	15	10	45	.28	7.1	0.045	1.1	6.25	MW	CG	N
0.480	12.19	71508S	1.00	25.4	.390	9.9	14	2.5	.47	12	6.9	31	.28	7.1	0.045	1.1	6.25	SST	CG	N
0.480	12.19	71522	1.00	25.4	.378	9.6	26	4.6	.53	13	14	61	.34	8.7	0.051	1.3	6.75	MW	CG	N
0.480	12.19	71522S	1.00	25.4	.378	9.6	22	3.9	.42	11	9.3	41	.34	8.7	0.051	1.3	6.75	SST	CG	N
0.480	12.19	71536	1.00	25.4	.370	9.4	35	6.1	.49	12	17	76	.38	9.6	0.055	1.4	6.88	MW	CG	N
0.480	12.19	71536S	1.00	25.4	.370	9.4	30	5.2	.39	9.9	12	52	.38	9.6	0.055	1.4	6.88	SST	CG	N
0.480	12.19	71550	1.00	25.4	.362	9.2	45													




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	F NISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.480	12.19	71537	1.25	31.8	.370	9.4	27	4.7	.63	16	17	76	.46	11.7	0.055	1.4	8.38	MW	CG	N
0.480	12.19	71537S	1.25	31.8	.370	9.4	23	4.0	.51	13	12	52	.46	11.7	0.055	1.4	8.38	SST	CG	N
0.480	12.19	71551	1.25	31.8	.362	9.2	35	6.1	.60	15	21	94	.51	12.9	0.059	1.5	8.63	MW	CG	N
0.480	12.19	71551S	1.25	31.8	.362	9.2	30	5.2	.48	12	14	63	.51	12.9	0.059	1.5	8.63	SST	CG	N
0.480	12.19	71565	1.25	31.8	.354	9.0	45	7.9	.57	14	25	113	.57	14.4	0.063	1.6	9.00	MW	CG	N
0.480	12.19	71565S	1.25	31.8	.354	9.0	38	6.7	.45	11	17	77	.57	14.4	0.063	1.6	9.00	SST	CG	N
0.480	12.19	71580	1.25	31.8	.346	8.8	59	10	.52	13	30	136	.60	15.3	0.067	1.7	9.00	MW	CG	N
0.480	12.19	71580S	1.25	31.8	.346	8.8	50	8.7	.42	11	21	92	.60	15.3	0.067	1.7	9.00	SST	CG	N
0.480	12.19	71593	1.25	31.8	.336	8.5	82	14	.44	11	36	160	.64	16.2	0.072	1.8	8.88	MW	CG	N
0.480	12.19	71593S	1.25	31.8	.336	8.5	70	12	.34	8.7	24	107	.64	16.2	0.072	1.8	8.88	SST	CG	N
0.480	12.19	71608	1.25	31.8	.332	8.4	92	16	.42	11	39	173	.67	16.9	0.074	1.9	9.00	MW	CG	N
0.480	12.19	71608S	1.25	31.8	.332	8.4	78	14	.33	8.4	26	116	.67	16.9	0.074	1.9	9.00	SST	CG	N
0.480	12.19	71623	1.25	31.8	.318	8.1	139	24	.36	9.2	50	224	.73	18.5	0.081	2.1	9.00	MW	CG	N
0.480	12.19	71623S	1.25	31.8	.318	8.1	118	21	.29	7.3	34	150	.73	18.5	0.081	2.1	9.00	SST	CG	N
0.480	12.19	71566	1.38	35.1	.354	9.0	43	7.5	.60	15	25	113	.59	15.0	0.063	1.6	9.38	MW	CG	N
0.480	12.19	71566S	1.38	35.1	.354	9.0	36	6.4	.48	12	17	77	.59	15.0	0.063	1.6	9.38	SST	CG	N
0.480	12.19	71471	1.50	38.1	.410	10.4	4.7	.82	1.0	26	4.8	21	.25	6.4	0.035	0.9	7.25	MW	CG	N
0.480	12.19	71471S	1.50	38.1	.410	10.4	4.0	.70	.82	21	3.3	15	.25	6.4	0.035	0.9	7.25	SST	CG	N
0.480	12.19	71482	1.50	38.1	.404	10.3	6.0	1.1	1.0	26	6.2	27	.29	7.5	0.038	1.0	7.75	MW	CG	N
0.480	12.19	71482S	1.50	38.1	.404	10.3	5.1	.89	.82	21	4.2	19	.29	7.5	0.038	1.0	7.75	SST	CG	N
0.480	12.19	71496	1.50	38.1	.396	10.1	8.5	1.5	.97	25	8.3	37	.35	8.8	0.042	1.1	8.25	MW	CG	N
0.480	12.19	71496S	1.50	38.1	.396	10.1	7.2	1.3	.77	20	5.6	25	.35	8.8	0.042	1.1	8.25	SST	CG	N
0.480	12.19	71510	1.50	38.1	.390	9.9	11	1.9	.92	23	10	45	.38	9.7	0.045	1.1	8.50	MW	CG	N
0.480	12.19	71510S	1.50	38.1	.390	9.9	9.4	1.6	.73	19	6.9	31	.38	9.7	0.045	1.1	8.50	SST	CG	N
0.480	12.19	71524	1.50	38.1	.378	9.6	17	2.9	.82	21	14	61	.48	12.1	0.051	1.3	9.38	MW	CG	N
0.480	12.19	71524S	1.50	38.1	.378	9.6	14	2.5	.65	17	9.3	41	.48	12.1	0.051	1.3	9.38	SST	CG	N
0.480	12.19	71538	1.50	38.1	.370	9.4	22	3.9	.78	20	17	76	.54	13.6	0.055	1.4	9.75	MW	CG	N
0.480	12.19	71538S	1.50	38.1	.370	9.4	19	3.3	.62	16	12	52	.54	13.6	0.055	1.4	9.75	SST	CG	N
0.480	12.19	71552	1.50	38.1	.362	9.2	29	5.0	.73	19	21	94	.60	15.2	0.059	1.5	10.1	MW	CG	N
0.480	12.19	71552S	1.50	38.1	.362	9.2	24	4.3	.58	15	14	63	.60	15.2	0.059	1.5	10.1	SST	CG	N
0.480	12.19	71567	1.50	38.1	.354	9.0	38	6.6	.68	17	25	113	.65	16.6	0.063	1.6	10.4	MW	CG	N
0.480	12.19	71567S	1.50	38.1	.354	9.0	32	5.6	.54	14	17	77	.65	16.6	0.063	1.6	10.4	SST	CG	N
0.480	12.19	71581	1.50	38.1	.346	8.8	48	8.4	.63	16	30	136	.70	17.9	0.067	1.7	10.5	MW	CG	N
0.480	12.19	71581S	1.50	38.1	.346	8.8	41	7.2	.51	13	21	92	.70	17.9	0.067	1.7	10.5	SST	CG	N
0.480	12.19	71594	1.50	38.1	.336	8.5	67	12	.54	14	36	160	.76	19.2	0.072	1.8	10.5	MW	CG	N
0.480	12.19	71594S	1.50	38.1	.336	8.5	57	10	.42	11	24	107	.76	19.2	0.072	1.8	10.5	SST	CG	N
0.480	12.19	71609	1.50	38.1	.332	8.4	75	13	.52	13	39	173	.78	19.7	0.074	1.9	10.5	MW	CG	N
0.480	12.19	71609S	1.50	38.1	.332	8.4	64	11	.41	10	26	116	.78	19.7	0.074	1.9	10.5	SST	CG	N
0.480	12.19	71624	1.50	38.1	.318	8.1	113	20	.45	11	50	224	.86	21.9	0.081	2.1	10.6	MW	CG	N
0.480	12.19	71624S	1.50	38.1	.318	8.1	96	17	.35	8.9	34	150	.86	21.9	0.081	2.1	10.6	SST	CG	N
0.480	12.19	71483	1.63	41.4	.404	10.3	5.5	.96	1.1	28	6.2	27	.31	8.0	0.038	1.0	8.25	MW	CG	N
0.480	12.19	71483S	1.63	41.4	.404	10.3	4.7	.82	.89	23	4.2	19	.31	8.0	0.038	1.0	8.25	SST	CG	N
0.480	12.19	71497	1.63	41.4	.396	10.1	7.7	1.3	1.1	27	8.3	37	.37	9.5	0.042	1.1	8.88	MW	CG	N
0.480	12.19	71497S	1.63	41.4	.396	10.1	6.5	1.1	.85	22	5.6	25	.37	9.5	0.042	1.1	8.88	SST	CG	N
0.480	12.19	71511	1.63	41.4	.390	9.9	9.8	1.7	1.0	26	10	45	.42	10.7	0.045	1.1	9.38	MW	CG	N
0.480	12.19	71511S	1.63	41.4	.390	9.9	8.3	1.5	.83	21	6.9	31	.42	10.7	0.045	1.1	9.38	SST	CG	N
0.480	12.19	71525	1.63	41.4	.378	9.6	15	2.6	.93	24	14	61	.53	13.4	0.051	1.3	10.4	MW	CG	N
0.480	12.19	71525S	1.63	41.4	.378	9.6	13	2.2	.74	19	9.3	41	.53	13.4	0.051	1.3	10.4	SST	CG	N
0.480	12.19	71539	1.63	41.4	.370	9.4	20	3.5	.86	22	17	76	.58	14.8	0.055	1.4	10.6	MW	CG	N
0.480	12.19	71539S	1.63	41.4	.370	9.4	17	3.0	.68	17	12	52	.58	14.8	0.055	1.4	10.6	SST	CG	N
0.480	12.19	71553	1.63	41.4	.362	9.2	26	4.5	.83	21	21	94	.66	16.7	0.059	1.5	11.1	MW	CG	N
0.480	12.19	71553S	1.63	41.4	.362	9.2	22	3.8	.66	17	14	63	.66	16.7	0.059	1.5	11.1	SST	CG	N
0.480	12.19	71568	1.63	41.4	.354	9.0	34	6.0	.75	19	25	113	.70	17.8	0.063	1.6	11.1	MW	CG	N
0.480	12.19	71568S	1.63	41.4	.354	9.0	29	5.1	.60	15	17	77	.70	17.8	0.063	1.6	11.1	SST	CG	N
0.480	12.19	71472	1.75	44.5	.410	10.4	4.0	.70	1.2	31	4.8	21	.28	7.2	0.035	0.9	8.13	MW	CG	N
0.480	12.19	71472S	1.75	44.5	.410	10.4	3.4	.60	.96	24	3.3	15	.28	7.2	0.035	0.9	8.13	SST	CG	N
0.480	12.19	71484	1.75	44.5	.404	10.3	5.2	.91	1.2	30	6.2	27	.33	8.3	0.038	1.0	8.63	MW	CG	N



1-800-237-5225
1-213-749-1466
Fax (213) 749-3802
www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.480	12.19	71485	2.00	50.8	.404	10.3	4.5	.79	1.4	35	6.2	27	.37	9.3	0.038	1.0	9.63	MW	CG	N
0.480	12.19	71485S	2.00	50.8	.404	10.3	3.8	.67	1.1	27	4.2	19	.37	9.3	0.038	1.0	9.63	SST	CG	N
0.480	12.19	71499	2.00	50.8	.396	10.1	6.4	1.1	1.3	33	8.3	37	.44	11.1	0.042	1.1	10.4	MW	CG	N
0.480	12.19	71499S	2.00	50.8	.396	10.1	5.4	.95	1.0	26	5.6	25	.44	11.1	0.042	1.1	10.4	SST	CG	N
0.480	12.19	71513	2.00	50.8	.390	9.9	8.1	1.4	1.3	32	10	45	.49	12.4	0.045	1.1	10.9	MW	CG	N
0.480	12.19	71513S	2.00	50.8	.390	9.9	6.8	1.2	1.0	25	6.9	31	.49	12.4	0.045	1.1	10.9	SST	CG	N
0.480	12.19	71527	2.00	50.8	.378	9.6	12	2.2	1.1	28	14	61	.61	15.4	0.051	1.3	11.9	MW	CG	N
0.480	12.19	71527S	2.00	50.8	.378	9.6	11	1.9	.88	22	9.3	41	.61	15.4	0.051	1.3	11.9	SST	CG	N
0.480	12.19	71541	2.00	50.8	.370	9.4	16	2.9	1.0	27	17	76	.69	17.5	0.055	1.4	12.5	MW	CG	N
0.480	12.19	71541S	2.00	50.8	.370	9.4	14	2.4	.83	21	12	52	.69	17.5	0.055	1.4	12.5	SST	CG	N
0.480	12.19	71555	2.00	50.8	.362	9.2	21	3.7	1.0	25	21	94	.77	19.5	0.059	1.5	13.0	MW	CG	N
0.480	12.19	71555S	2.00	50.8	.362	9.2	18	3.1	.79	20	14	63	.77	19.5	0.059	1.5	13.0	SST	CG	N
0.480	12.19	71570	2.00	50.8	.354	9.0	27	4.8	.93	24	25	113	.84	21.4	0.063	1.6	13.4	MW	CG	N
0.480	12.19	71570S	2.00	50.8	.354	9.0	23	4.1	.74	19	17	77	.84	21.4	0.063	1.6	13.4	SST	CG	N
0.480	12.19	71583	2.00	50.8	.346	8.8	35	6.2	.87	22	30	136	.91	23.2	0.067	1.7	13.6	MW	CG	N
0.480	12.19	71583S	2.00	50.8	.346	8.8	30	5.2	.69	18	21	92	.91	23.2	0.067	1.7	13.6	SST	CG	N
0.480	12.19	71596	2.00	50.8	.336	8.5	49	8.6	.73	19	36	160	.98	24.9	0.072	1.8	13.6	MW	CG	N
0.480	12.19	71596S	2.00	50.8	.336	8.5	42	7.3	.58	15	24	107	.98	24.9	0.072	1.8	13.6	SST	CG	N
0.480	12.19	71611	2.00	50.8	.332	8.4	55	9.6	.71	18	39	173	1.02	25.8	0.074	1.9	13.8	MW	CG	N
0.480	12.19	71611S	2.00	50.8	.332	8.4	47	8.2	.56	14	26	116	1.02	25.8	0.074	1.9	13.8	SST	CG	N
0.480	12.19	71626	2.00	50.8	.318	8.1	82	14	.61	16	50	224	1.12	28.5	0.081	2.1	13.9	MW	CG	N
0.480	12.19	71626S	2.00	50.8	.318	8.1	70	12	.48	12	34	150	1.12	28.5	0.081	2.1	13.9	SST	CG	N
0.480	12.19	71486	2.25	57.2	.404	10.3	4.2	.73	1.5	37	6.2	27	.39	9.9	0.038	1.0	10.3	MW	CG	N
0.480	12.19	71486S	2.25	57.2	.404	10.3	3.6	.62	1.2	30	4.2	19	.39	9.9	0.038	1.0	10.3	SST	CG	N
0.480	12.19	71500	2.25	57.2	.396	10.1	5.7	1.0	1.5	37	8.3	37	.48	12.1	0.042	1.1	11.4	MW	CG	N
0.480	12.19	71500S	2.25	57.2	.396	10.1	4.8	.85	1.2	29	5.6	25	.48	12.1	0.042	1.1	11.4	SST	CG	N
0.480	12.19	71514	2.25	57.2	.390	9.9	7.1	1.2	1.4	37	10	45	.55	13.9	0.045	1.1	12.1	MW	CG	N
0.480	12.19	71514S	2.25	57.2	.390	9.9	6.0	1.0	1.1	29	6.9	31	.55	13.9	0.045	1.1	12.1	SST	CG	N
0.480	12.19	71528	2.25	57.2	.378	9.6	11	1.9	1.3	32	14	61	.68	17.2	0.051	1.3	13.3	MW	CG	N
0.480	12.19	71528S	2.25	57.2	.378	9.6	9.3	1.6	1.0	25	9.3	41	.68	17.2	0.051	1.3	13.3	SST	CG	N
0.480	12.19	71542	2.25	57.2	.370	9.4	15	2.5	1.2	30	17	76	.76	19.2	0.055	1.4	13.8	MW	CG	N
0.480	12.19	71542S	2.25	57.2	.370	9.4	12	2.2	.94	24	12	52	.76	19.2	0.055	1.4	13.8	SST	CG	N
0.480	12.19	71556	2.25	57.2	.362	9.2	19	3.3	1.1	29	21	94	.86	21.7	0.059	1.5	14.5	MW	CG	N
0.480	12.19	71556S	2.25	57.2	.362	9.2	16	2.8	.90	23	14	63	.86	21.7	0.059	1.5	14.5	SST	CG	N
0.480	12.19	71571	2.25	57.2	.354	9.0	24	4.3	1.0	27	25	113	.94	23.8	0.063	1.6	14.9	MW	CG	N
0.480	12.19	71571S	2.25	57.2	.354	9.0	21	3.6	.84	21	17	77	.94	23.8	0.063	1.6	14.9	SST	CG	N
0.480	12.19	71584	2.25	57.2	.346	8.8	31	5.4	.98	25	30	136	1.02	26.0	0.067	1.7	15.3	MW	CG	N
0.480	12.19	71584S	2.25	57.2	.346	8.8	26	4.6	.78	20	21	92	1.02	26.0	0.067	1.7	15.3	SST	CG	N
0.480	12.19	71597	2.25	57.2	.336	8.5	43	7.6	.83	21	36	160	1.09	27.7	0.072	1.8	15.1	MW	CG	N
0.480	12.19	71597S	2.25	57.2	.336	8.5	37	6.4	.66	17	24	107	1.09	27.7	0.072	1.8	15.1	SST	CG	N
0.480	12.19	71612	2.25	57.2	.332	8.4	48	8.5	.80	20	39	173	1.13	28.7	0.074	1.9	15.3	MW	CG	N
0.480	12.19	71612S	2.25	57.2	.332	8.4	41	7.2	.63	16	26	116	1.13	28.7	0.074	1.9	15.3	SST	CG	N
0.480	12.19	71627	2.25	57.2	.318	8.1	72	13	.70	18	50	224	1.26	31.9	0.081	2.1	15.5	MW	CG	N
0.480	12.19	71627S	2.25	57.2	.318	8.1	61	11	.55	14	34	150	1.26	31.9	0.081	2.1	15.5	SST	CG	N
0.480	12.19	71474	2.50	63.5	.410	10.4	2.8	.49	1.7	44	4.8	21	.38	9.6	0.035	0.9	10.8	MW	CG	N
0.480	12.19	71474S	2.50	63.5	.410	10.4	2.4	.42	1.4	35	3.3	15	.38	9.6	0.035	0.9	10.8	SST	CG	N
0.480	12.19	71487	2.50	63.5	.404	10.3	3.8	.66	1.6	42	6.2	27	.43	10.9	0.038	1.0	11.3	MW	CG	N
0.480	12.19	71487S	2.50	63.5	.404	10.3	3.2	.56	1.3	33	4.2	19	.43	10.9	0.038	1.0	11.3	SST	CG	N
0.480	12.19	71501	2.50	63.5	.396	10.1	5.4	.94	1.5	39	8.3	37	.50	12.8	0.042	1.1	12.0	MW	CG	N
0.480	12.19	71501S	2.50	63.5	.396	10.1	4.5	.80	1.2	31	5.6	25	.50	12.8	0.042	1.1	12.0	SST	CG	N
0.480	12.19	71515	2.50	63.5	.390	9.9	6.4	1.1	1.6	40	10	45	.60	15.1	0.045	1.1	13.3	MW	CG	N
0.480	12.19	71515S	2.50	63.5	.390	9.9	5.4	.95	1.3	32	6.9	31	.60	15.1	0.045	1.1	13.3	SST	CG	N
0.480	12.19	71529	2.50	63.5	.378	9.6	9.9	1.7	1.4	35	14	61	.74	18.8	0.051	1.3	14.5	MW	CG	N
0.480	12.19	71529S	2.50	63.5	.378	9.6	8.4	1.5	1.1	28	9.3	41	.74	18.8	0.051	1.3	14.5	SST	CG	N
0.480	12.19	71543	2.50	63.5	.370	9.4	13	2.3	1.3	34	17	76	.84	21.3	0.055	1.4	15.3	MW	CG	N
0.480	12.19	71543S	2.50	63.5	.370	9.4	11	1.9	1.1	27	12	52	.84	21.3	0.055	1.4	15.3	SST	CG	N
0.480	12.19	71557	2.50	63.5	.362	9.2	17	2.9	1.3	32	21	94	.95	24.2	0.059	1.5	16.1	MW	CG	N
0.480	12.19	71557S	2.50	63.5	.362	9.2	14													




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	F NISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.480	12.19	71573	2.75	69.9	.354	9.0	20	3.5	1.3	33	25	113	1.12	28.4	0.063	1.6	17.8	MW	CG	N
0.480	12.19	71573S	2.75	69.9	.354	9.0	17	3.0	1.0	26	17	77	1.12	28.4	0.063	1.6	17.8	SST	CG	N
0.480	12.19	71586	2.75	69.9	.346	8.8	25	4.4	1.2	31	30	136	1.23	31.3	0.067	1.7	18.4	MW	CG	N
0.480	12.19	71586S	2.75	69.9	.346	8.8	21	3.7	.97	25	21	92	1.23	31.3	0.067	1.7	18.4	SST	CG	N
0.480	12.19	71599	2.75	69.9	.336	8.5	35	6.1	1.0	26	36	160	1.31	33.4	0.072	1.8	18.3	MW	CG	N
0.480	12.19	71599S	2.75	69.9	.336	8.5	30	5.2	.81	21	24	107	1.31	33.4	0.072	1.8	18.3	SST	CG	N
0.480	12.19	71614	2.75	69.9	.332	8.4	39	6.8	.99	25	39	173	1.37	34.8	0.074	1.9	18.5	MW	CG	N
0.480	12.19	71614S	2.75	69.9	.332	8.4	33	5.8	.78	20	26	116	1.37	34.8	0.074	1.9	18.5	SST	CG	N
0.480	12.19	71629	2.75	69.9	.318	8.1	58	10	.87	22	50	224	1.52	38.6	0.081	2.1	18.8	MW	CG	N
0.480	12.19	71629S	2.75	69.9	.318	8.1	50	8.7	.68	17	34	150	1.52	38.6	0.081	2.1	18.8	SST	CG	N
0.480	12.19	71475	3.00	76.2	.410	10.4	2.3	.40	2.1	53	4.8	21	.44	11.2	0.035	0.9	12.6	MW	CG	N
0.480	12.19	71475S	3.00	76.2	.410	10.4	2.0	.34	1.7	42	3.3	15	.44	11.2	0.035	0.9	12.6	SST	CG	N
0.480	12.19	71489	3.00	76.2	.404	10.3	3.1	.55	2.0	50	6.2	27	.50	12.7	0.038	1.0	13.1	MW	CG	N
0.480	12.19	71489S	3.00	76.2	.404	10.3	2.6	.46	1.6	40	4.2	19	.50	12.7	0.038	1.0	13.1	SST	CG	N
0.480	12.19	71503	3.00	76.2	.396	10.1	4.4	.77	1.9	48	8.3	37	.59	14.9	0.042	1.1	14.0	MW	CG	N
0.480	12.19	71503S	3.00	76.2	.396	10.1	3.8	.66	1.5	38	5.6	25	.59	14.9	0.042	1.1	14.0	SST	CG	N
0.480	12.19	12726	3.00	76.2	.390	9.9	5.1	.89	1.3	34	6.9	31	.64	16.3	0.045	1.1	14.3	SST	CG	N
0.480	12.19	71517	3.00	76.2	.390	9.9	5.3	.93	1.9	49	10	45	.70	17.7	0.045	1.1	15.5	MW	CG	N
0.480	12.19	71517S	3.00	76.2	.390	9.9	4.5	.79	1.5	39	6.9	31	.70	17.7	0.045	1.1	15.5	SST	CG	N
0.480	12.19	71531	3.00	76.2	.378	9.6	8.0	1.4	1.7	44	14	61	.89	22.5	0.051	1.3	17.4	MW	CG	N
0.480	12.19	71531S	3.00	76.2	.378	9.6	6.8	1.2	1.4	35	9.3	41	.89	22.5	0.051	1.3	17.4	SST	CG	N
0.480	12.19	71545	3.00	76.2	.370	9.4	11	1.9	1.6	41	17	76	.99	25.1	0.055	1.4	18.0	MW	CG	N
0.480	12.19	71545S	3.00	76.2	.370	9.4	9.1	1.6	1.3	32	12	52	.99	25.1	0.055	1.4	18.0	SST	CG	N
0.480	12.19	71559	3.00	76.2	.362	9.2	14	2.4	1.5	39	21	94	1.11	28.3	0.059	1.5	18.9	MW	CG	N
0.480	12.19	71559S	3.00	76.2	.362	9.2	12	2.1	1.2	31	14	63	1.11	28.3	0.059	1.5	18.9	SST	CG	N
0.480	12.19	71574	3.00	76.2	.354	9.0	18	3.1	1.4	37	25	113	1.24	31.6	0.063	1.6	19.8	MW	CG	N
0.480	12.19	71574S	3.00	76.2	.354	9.0	15	2.6	1.2	29	17	77	1.24	31.6	0.063	1.6	19.8	SST	CG	N
0.480	12.19	71587	3.00	76.2	.346	8.8	23	4.0	1.3	34	30	136	1.33	33.8	0.067	1.7	19.9	MW	CG	N
0.480	12.19	71587S	3.00	76.2	.346	8.8	20	3.4	1.1	27	21	92	1.33	33.8	0.067	1.7	19.9	SST	CG	N
0.480	12.19	71600	3.00	76.2	.336	8.5	32	5.6	1.1	29	36	160	1.43	36.3	0.072	1.8	19.9	MW	CG	N
0.480	12.19	71600S	3.00	76.2	.336	8.5	27	4.7	.89	23	24	107	1.43	36.3	0.072	1.8	19.9	SST	CG	N
0.480	12.19	71615	3.00	76.2	.332	8.4	36	6.3	1.1	28	39	173	1.48	37.6	0.074	1.9	20.0	MW	CG	N
0.480	12.19	71615S	3.00	76.2	.332	8.4	30	5.3	.86	22	26	116	1.48	37.6	0.074	1.9	20.0	SST	CG	N
0.480	12.19	71630	3.00	76.2	.318	8.1	53	9.3	.95	24	50	224	1.64	41.7	0.081	2.1	20.3	MW	CG	N
0.480	12.19	71630S	3.00	76.2	.318	8.1	45	7.9	.75	19	34	150	1.64	41.7	0.081	2.1	20.3	SST	CG	N
0.480	12.19	71601	3.25	82.6	.336	8.5	29	5.1	1.2	31	36	160	1.54	39.1	0.072	1.8	21.4	MW	CG	N
0.480	12.19	71601S	3.25	82.6	.336	8.5	25	4.4	.97	25	24	107	1.54	39.1	0.072	1.8	21.4	SST	CG	N
0.480	12.19	71616	3.25	82.6	.332	8.4	33	5.7	1.2	30	39	173	1.60	40.6	0.074	1.9	21.6	MW	CG	N
0.480	12.19	71616S	3.25	82.6	.332	8.4	28	4.9	.93	24	26	116	1.60	40.6	0.074	1.9	21.6	SST	CG	N
0.480	12.19	71631	3.25	82.6	.318	8.1	49	8.6	1.0	26	50	224	1.77	45.0	0.081	2.1	21.9	MW	CG	N
0.480	12.19	71631S	3.25	82.6	.318	8.1	42	7.3	.81	21	34	150	1.77	45.0	0.081	2.1	21.9	SST	CG	N
0.480	12.19	71602	3.50	88.9	.336	8.5	27	4.7	1.3	34	36	160	1.66	42.1	0.072	1.8	23.0	MW	CG	N
0.480	12.19	71602S	3.50	88.9	.336	8.5	23	4.0	1.0	27	24	107	1.66	42.1	0.072	1.8	23.0	SST	CG	N
0.480	12.19	71617	3.50	88.9	.332	8.4	30	5.3	1.3	32	39	173	1.72	43.7	0.074	1.9	23.3	MW	CG	N
0.480	12.19	71617S	3.50	88.9	.332	8.4	26	4.5	1.0	26	26	116	1.72	43.7	0.074	1.9	23.3	SST	CG	N
0.480	12.19	71632	3.50	88.9	.318	8.1	45	7.9	1.1	28	50	224	1.90	48.3	0.081	2.1	23.5	MW	CG	N
0.480	12.19	71632S	3.50	88.9	.318	8.1	38	6.7	.88	22	34	150	1.90	48.3	0.081	2.1	23.5	SST	CG	N
0.484	12.29	H-35	.25	6.4	.388	9.9	92	16	.10	2.4	8.8	39	.14	3.7	0.048	1.2	3.00	SPR	CG	Z
0.484	12.29	AA-63	.25	6.4	.384	9.8	97	17	.09	2.3	8.7	39	.15	3.8	0.050	1.3	3.00	SST	CG	N
0.484	12.29	UU-69	.25	6.4	.376	9.6	134	23	.08	2.1	11	49	.16	4.1	0.054	1.4	3.00	SST	CG	N
0.484	12.29	A10-50	.31	7.9	.424	10.8	12	2.2	.22	5.6	2.8	12	.09	2.3	0.030	0.8	3.00	MW	CG	GI
0.484	12.29	S-1575	.34	8.7	.404	10.3	37	6.5	.13	3.3	4.8	21	.16	4.1	0.040	1.0	3.00	SST	C	N
0.484	12.29	L-6	.34	8.7	.390	9.9	84	15	.10	2.5	8.3	37	.14	3.6	0.047	1.2	3.00	SPR	CG	Z
0.484	12.29	S-1042	.34	8.7	.360	9.1	167	29	.10	2.5	16	73	.22	5.5	0.062	1.6	3.50	SST	CG	N
0.484	12.29	00-86	.38	9.5	.414	10.5	10	1.8	.24	6.0	2.4	11	.14	3.6	0.035	0.9	4.00	SST	CG	N
0.484	12.29	GG-88	.38	9.5	.394	10.0	61	11	.11	2.9	6.8	30	.18	4.6	0.045	1.1	3.00	SST	C	N
0.484	12.29	S-45	.41	10.3	.402	10.2	16	2.8	.18	4.6	2.9	13								




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.484	12.29	XX-37	.56	14.3	.390	9.9	28	4.9	.28	7.1	7.8	35	.28	7.2	0.047	1.2	5.00	SPR	C	Z
0.484	12.29	10993	.56	14.3	.372	9.4	90	16	.14	3.6	13	57	.28	7.1	0.056	1.4	4.00	HD	C	Z
0.484	12.29	N-134	.59	15.1	.420	10.7	3.3	.57	.37	9.4	1.2	5.4	.22	5.7	0.032	0.8	7.00	SPR	CG	N
0.484	12.29	W-35	.59	15.1	.414	10.5	5.2	.91	.35	8.8	1.8	8.0	.25	6.2	0.035	0.9	6.00	SST	C	N
0.484	12.29	11197	.63	15.9	.420	10.7	3.9	.68	.41	10	1.6	7.0	.22	5.5	0.032	0.8	5.75	SST	C	N
0.484	12.29	10781	.63	15.9	.384	9.8	44	7.7	.21	5.3	9.3	41	.23	5.7	0.050	1.3	4.50	SPR	CG	N
0.484	12.29	PP-87	.63	15.9	.384	9.8	31	5.5	.29	7.5	9.3	41	.28	7.0	0.050	1.3	5.50	SPR	CG	Z
0.484	12.29	2625	.63	15.9	.372	9.4	72	13	.25	6.3	18	80	.25	6.4	0.056	1.4	4.50	MW	CG	Z
0.484	12.29	B9-12	.69	17.4	.436	11.1	3.7	.64	.47	12	1.7	7.7	.10	2.6	0.024	0.6	3.33	MW	CG	Z
0.484	12.29	S-866	.72	18.2	.414	10.5	5.2	.91	.51	13	2.6	12	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.484	12.29	S-1401	.72	18.2	.360	9.1	82	14	.20	5.1	16	73	.31	7.9	0.062	1.6	5.00	SST	CG	N
0.484	12.29	S-1560	.72	18.2	.304	7.7	383	67	.11	2.9	43	192	.50	12.6	0.090	2.3	5.50	SST	CG	N
0.484	12.29	W-60	.75	19.1	.448	11.4	.14	.02	.53	13	.07	.33	.22	5.6	0.018	0.5	11.3	SST	C	N
0.484	12.29	N-85	.75	19.1	.436	11.1	1.4	.25	.61	15	.86	3.8	.14	3.7	0.024	0.6	5.00	SST	C	N
0.484	12.29	FF-35	.75	19.1	.432	11.0	2.0	.35	.59	15	1.2	5.2	.16	4.0	0.026	0.7	5.00	SST	C	N
0.484	12.29	II-75	.75	19.1	.404	10.3	9.3	1.6	.47	12	4.4	19	.28	7.1	0.040	1.0	6.00	SST	C	N
0.484	12.29	JJ-97	.75	19.1	.376	9.6	38	6.7	.30	7.7	12	52	.32	8.2	0.054	1.4	6.00	SPR	CG	GI
0.484	12.29	10934	.75	19.1	.358	9.1	71	13	.26	6.5	18	81	.39	10.0	0.063	1.6	6.25	SPR	CG	Z
0.484	12.29	3594	.75	19.1	.340	8.6	138	24	.26	6.6	36	159	.43	11.0	0.072	1.8	6.00	MW	CG	GI
0.484	12.29	S-1539	.78	19.8	.426	10.8	2.0	.35	.59	15	1.2	5.1	.20	5.0	0.029	0.7	6.75	SST	CG	N
0.484	12.29	10899	.78	19.8	.334	8.5	285	50	.10	2.6	29	128	.33	8.3	0.075	1.9	4.33	SPR	CG	N
0.484	12.29	12425	.81	20.6	.430	10.9	3.2	.56	.66	17	2.1	9.4	.15	3.8	0.027	0.7	4.50	MW	C	N
0.484	12.29	1653	.81	20.6	.350	8.9	80	14	.27	6.9	22	97	.47	11.9	0.067	1.7	7.00	HD	CG	Z
0.484	12.29	12215	.84	21.4	.424	10.8	3.1	.54	.63	16	2.0	8.8	.21	5.3	0.030	0.8	6.00	MW	C	Z
0.484	12.29	W-64	.84	21.4	.416	10.6	6.2	1.1	.50	13	3.1	14	.20	5.2	0.034	0.9	5.00	SST	C	N
0.484	12.29	10557	.84	21.4	.346	8.8	107	19	.22	5.6	24	106	.43	10.9	0.069	1.8	6.25	SPR	CG	Z
0.484	12.29	I-31	.88	22.2	.446	11.3	.31	.05	.70	18	.22	.97	.17	4.3	0.019	0.5	8.00	MW	C	N
0.484	12.29	H-90	.88	22.2	.440	11.2	.31	.05	.59	15	.18	.82	.28	7.1	0.022	0.6	11.8	SST	C	N
0.484	12.29	4285	.88	22.2	.360	9.1	47	8.2	.37	9.4	17	77	.50	12.6	0.062	1.6	8.00	SPR	CG	Z
0.484	12.29	CC-1	.88	22.2	.300	7.6	270	47	.17	4.3	46	204	.69	17.5	0.092	2.3	7.50	SST	CG	N
0.484	12.29	G-75	.88	22.2	.266	6.8	641	112	.003	.08	1.9	8.6	.87	22.1	0.109	2.8	8.00	HD	CG	N
0.484	12.29	PP-80	.91	23.0	.418	10.6	4.1	.72	.66	17	2.7	12	.25	6.3	0.033	0.8	6.50	SPR	C	N
0.484	12.29	B12-21	.94	23.8	.402	10.2	12	2.0	.47	12	5.5	25	.25	6.2	0.041	1.0	6.00	SPR	CG	N
0.484	12.29	YY-53	.94	23.8	.394	10.0	15	2.7	.45	11	6.8	30	.32	8.0	0.045	1.1	6.00	SST	C	N
0.484	12.29	TT-40	.94	23.8	.392	10.0	18	3.1	.41	10	7.3	32	.26	6.7	0.046	1.2	5.75	SST	CG	N
0.484	12.29	S-399	.94	23.8	.358	9.1	48	8.4	.36	9.1	17	76	.47	12.0	0.063	1.6	7.50	SST	CG	N
0.484	12.29	II-90	.94	23.8	.350	8.9	67	12	.33	8.3	22	97	.54	13.6	0.067	1.7	8.00	SPR	CG	N
0.484	12.29	1525	1.00	25.4	.418	10.6	2.1	.36	.60	15	1.2	5.5	.40	10.1	0.033	0.8	11.0	SPR	C	Z
0.484	12.29	S-3135	1.00	25.4	.410	10.4	6.6	1.1	.58	15	3.8	17	.22	5.6	0.037	0.9	6.00	SST	CG	N
0.484	12.29	10491	1.00	25.4	.394	10.0	14	2.4	.52	13	7.3	32	.32	8.0	0.045	1.1	7.00	SPR	CG	Z
0.484	12.29	1885	1.00	25.4	.394	10.0	17	3.1	.58	15	10	45	.27	6.9	0.045	1.1	6.00	MW	CG	Z
0.484	12.29	11815	1.00	25.4	.388	9.9	15	2.7	.57	15	8.8	39	.38	9.8	0.048	1.2	8.00	SPR	CG	Z
0.484	12.29	3088	1.00	25.4	.384	9.8	17	3.0	.55	14	9.3	41	.43	10.8	0.050	1.3	8.50	SPR	CG	Z
0.484	12.29	00-66	1.00	25.4	.384	9.8	27	4.8	.34	8.6	9.3	41	.30	7.6	0.050	1.3	6.00	SPR	CG	N
0.484	12.29	DD-94	1.00	25.4	.384	9.8	24	4.3	.38	9.6	9.3	41	.33	8.3	0.050	1.3	6.50	SPR	CG	N
0.484	12.29	12304	1.00	25.4	.374	9.5	33	5.8	.37	9.3	12	54	.44	11.2	0.055	1.4	7.00	SPR	C	Z
0.484	12.29	TT-42	1.00	25.4	.360	9.1	41	7.2	.40	10	16	73	.50	12.6	0.062	1.6	8.00	SST	CG	N
0.484	12.29	YY-31	1.00	25.4	.360	9.1	94	16	.18	4.7	17	77	.31	7.9	0.062	1.6	5.00	SPR	CG	Z
0.484	12.29	10598	1.00	25.4	.356	9.0	54	9.5	.35	8.9	19	85	.51	13.0	0.064	1.6	8.00	SPR	CG	Z
0.484	12.29	Z-47	1.00	25.4	.294	7.5	332	58	.16	4.2	54	241	.76	19.3	0.095	2.4	8.00	SPR	CG	N
0.484	12.29	RR-60	1.03	26.2	.274	7.0	535	94	.13	3.4	72	319	.84	21.3	0.105	2.7	8.00	SPR	CG	Z
0.484	12.29	A-94	1.06	27.0	.300	7.6	270	47	.17	4.3	46	204	.69	17.5	0.092	2.3	7.50	SST	CG	N
0.484	12.29	B5-35	1.09	27.8	.400	10.2	10	1.8	.57	15	5.9	26	.34	8.5	0.042	1.1	7.00	SPR	C	N
0.484	12.29	L-21	1.09	27.8	.390	9.9	16	2.8	.48	12	7.7	34	.31	7.8	0.047	1.2	6.50	SST	CG	N
0.484	12.29	S-1092	1.13	28.6	.434	11.0	1.0	.18	.93	23	.93	4.2	.20	5.1	0.025	0.6	7.00	SST	C	N
0.484	12.29	A-35	1.13	28.6	.420	10.7	1.8	.32	.74	19	1.3	6.0	.38	9.8	0.032	0.8	11.0	SPR	C	N
0.484	12.29	H-47	1.13	28.6	.386	9.8	14	2.5	.65	16	9.3	42	.44	11.2	0.049	1.2	9.00	SPR	CG	Z
0.484	12.29	XX-68	1.13	28.6	.382	9.7	22	3.8	.45	11	9.8	44	.43	11.0	0.051	1.3	7.50	SPR	C	Z
0.484	12.29	10351	1.16	29.4	.360	9.1	35	6.2	.47	12	17	74	.68	17.3	0.062	1.6	10.0	SPR	C	Z
0.484	12.29	S-1126	1.19	30.2	.426	10.8	1.7	.30	.94	24	1.6	7.1	.25	6.3	0.029	0.7	7.50	SST	C	N
0.484	12.29	H-39	1.19	30.2	.340	8.6	60	11	.40	10	24	106	.72	18.3	0.072	1.8	10.0	SST	CG	N
0.484	12.29	A-39	1.22	31.0	.420	10.7	2.9	.51	.89	23	2.6	11	.26	6.5	0.032	0.8	7.00	SST	C	N
0.484	12.29	S-822	1.22	31.0	.390	9.9	6.8	1.2	.62	16	4.2	19	.60	15.2	0.047	1.2	12.8	SST	CG	N
0.484	12.29	10558	1.22	31.0	.356	9.0	42	7.4	.45	12	19	85	.69	17.5	0.064	1.6	9.75	SPR	C	Z
0.484	12.29	S-294	1.25	31.8	.416	10.6	4.6	.80	.67	17	3.1	14	.24	6.0	0.034	0.9	6.00	SST	C	N
0.484	12.29	10695	1.25	31.8	.376	9.6	28	4.9	.42	11	12	52	.41	10.3	0.054	1.4	7.50	SPR	CG	Z
0.484	12.29	11403	1.25	31.8	.376	9.6	21	3.7	.52	13	11	49	.51	13.0	0.054	1.4	8.50	SST	C	N
0.484	12.29	A11-31	1.28	32.5	.392	10.0	13	2.3	.55	14	7.3	32	.33	8.3	0.046	1.2	7.00	SST	CG	N



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.484	12.29	B14-47	1.41	35.7	.418	10.6	2.9	.50	1.1	27	3.0	14	.28	7.1	0.033	0.8	8.50	SPR	CG	N
0.484	12.29	B9-8	1.44	36.5	.396	10.1	14	2.5	.48	12	6.8	30	.29	7.3	0.044	1.1	6.50	SPR	CG	Z
0.484	12.29	YY-60	1.44	36.5	.392	10.0	13	2.2	.61	15	7.8	34	.41	10.5	0.046	1.2	8.00	SPR	C	Z
0.484	12.29	A15-66	1.47	37.3	.364	9.2	29	5.1	.51	13	15	66	.57	14.5	0.060	1.5	9.50	SST	CG	N
0.484	12.29	2620	1.47	37.3	.356	9.0	33	5.7	.59	15	19	85	.77	19.5	0.064	1.6	12.0	HD	CG	Z
0.484	12.29	S-1376	1.50	38.1	.414	10.5	1.3	.23	.84	21	1.1	4.9	.66	16.7	0.035	0.9	17.8	SST	C	N
0.484	12.29	3570	1.50	38.1	.408	10.4	4.2	.74	1.0	27	4.4	20	.42	10.6	0.038	1.0	10.0	SPR	C	Z
0.484	12.29	12219	1.50	38.1	.408	10.4	6.8	1.2	.65	17	4.4	20	.27	6.8	0.038	1.0	7.00	SPR	CG	Z
0.484	12.29	3665	1.50	38.1	.404	10.3	6.7	1.2	.76	19	5.1	23	.37	9.4	0.040	1.0	8.25	SPR	C	Z
0.484	12.29	S-1490	1.50	38.1	.402	10.2	6.5	1.1	.80	20	5.2	23	.34	8.6	0.041	1.0	8.25	SST	CG	N
0.484	12.29	A13-40	1.50	38.1	.390	9.9	14	2.5	.59	15	8.3	37	.38	9.6	0.047	1.2	8.00	SPR	CG	GI
0.484	12.29	S-1413	1.50	38.1	.382	9.7	10	1.8	.84	21	8.7	39	.66	16.8	0.051	1.3	12.0	SST	C	N
0.484	12.29	2729	1.50	38.1	.376	9.6	17	3.0	.68	17	12	52	.59	15.1	0.054	1.4	11.0	HD	CG	Z
0.484	12.29	H-42	1.50	38.1	.370	9.4	22	3.8	.63	16	14	60	.68	17.4	0.057	1.4	11.0	SPR	C	Z
0.484	12.29	PP-56	1.50	38.1	.364	9.2	31	5.4	.52	13	16	70	.60	15.2	0.060	1.5	10.0	SPR	CG	GI
0.484	12.29	B9-69	1.50	38.1	.364	9.2	20	3.6	.66	17	13	60	.84	21.3	0.060	1.5	14.0	SPR	CG	N
0.484	12.29	F-48	1.50	38.1	.360	9.1	35	6.2	.49	12	17	77	.62	15.7	0.062	1.6	10.0	SPR	CG	Z
0.484	12.29	3153	1.50	38.1	.340	8.6	63	11	.40	10	26	113	.77	19.7	0.072	1.8	10.8	SPR	CG	Z
0.484	12.29	Q-75	1.50	38.1	.260	6.6	628	110	.13	3.4	83	369	1.01	25.6	0.112	2.8	9.00	SPR	CG	Z
0.484	12.29	O-96	1.53	38.9	.432	11.0	.49	.09	1.1	28	.53	2.4	.44	11.2	0.026	0.7	16.0	MW	C	N
0.484	12.29	B15-36	1.53	38.9	.388	9.9	6.8	1.2	.86	22	5.8	26	.67	17.1	0.048	1.2	14.0	SST	CG	N
0.484	12.29	S-223	1.56	39.7	.412	10.5	2.9	.51	1.2	31	3.5	16	.36	9.1	0.036	0.9	10.0	SST	CG	N
0.484	12.29	4286	1.56	39.7	.374	9.5	16	2.8	.77	20	12	54	.69	17.5	0.055	1.4	12.5	SPR	CG	Z
0.484	12.29	10039	1.59	40.5	.372	9.4	17	3.0	.75	19	13	57	.70	17.8	0.056	1.4	12.5	SPR	CG	N
0.484	12.29	10833	1.63	41.3	.404	10.3	8.0	1.4	.64	16	5.1	23	.29	7.4	0.040	1.0	7.25	SPR	CG	Z
0.484	12.29	J-40	1.63	41.3	.384	9.8	16	2.8	.55	14	8.7	39	.40	10.2	0.050	1.3	8.00	SST	CG	N
0.484	12.29	11244	1.63	41.3	.360	9.1	33	5.8	.52	13	17	77	.65	16.5	0.062	1.6	10.5	SPR	CG	Z
0.484	12.29	S-1268	1.63	41.3	.340	8.6	51	8.9	.47	12	24	106	.83	21.0	0.072	1.8	11.5	SST	CG	N
0.484	12.29	4226	1.63	41.3	.324	8.2	85	15	.41	10	35	154	1.00	25.4	0.080	2.0	12.5	SPR	CG	GI
0.484	12.29	10356	1.69	42.8	.408	10.4	6.8	1.2	.65	17	4.4	20	.30	7.7	0.038	1.0	7.00	SPR	C	Z
0.484	12.29	10320	1.69	42.8	.360	9.1	29	5.1	.60	15	17	77	.79	20.1	0.062	1.6	11.8	SPR	C	Z
0.484	12.29	S-843	1.69	42.8	.340	8.6	47	8.2	.51	13	24	106	.90	22.9	0.072	1.8	12.5	SST	CG	N
0.484	12.29	II-40	1.69	42.8	.264	6.7	366	64	.22	5.5	79	351	1.43	36.3	0.110	2.8	13.0	SPR	CG	N
0.484	12.29	11270	1.72	43.6	.288	7.3	210	37	.28	7.2	59	263	1.27	32.4	0.098	2.5	13.0	SPR	CG	Z
0.484	12.29	2888	1.75	44.5	.360	9.1	24	4.1	.74	19	17	77	.93	23.6	0.062	1.6	14.0	SPR	C	Z
0.484	12.29	3240	1.75	44.5	.324	8.2	112	20	.31	7.9	35	154	.80	20.3	0.080	2.0	10.0	SPR	CG	Z
0.484	12.29	10493	1.81	46.0	.388	9.9	8.4	1.5	1.1	27	8.8	39	.62	15.8	0.048	1.2	13.0	SPR	CG	GI
0.484	12.29	10282	1.81	46.0	.376	9.6	19	3.4	.60	15	12	52	.59	15.1	0.054	1.4	10.0	SPR	C	Z
0.484	12.29	XX-66	1.81	46.0	.360	9.1	28	4.9	.62	16	17	77	.74	18.9	0.062	1.6	12.0	SPR	CG	Z
0.484	12.29	H-46	1.81	46.0	.360	9.1	19	3.3	.87	22	16	73	.93	23.6	0.062	1.6	15.0	SST	CG	N
0.484	12.29	2790	1.84	46.8	.356	9.0	33	5.7	.59	15	19	85	.83	21.1	0.064	1.6	12.0	SPR	C	Z
0.484	12.29	10413	1.88	47.6	.376	9.6	15	2.7	.75	19	12	52	.65	16.5	0.054	1.4	12.0	SPR	CG	Z
0.484	12.29	10723	1.88	47.6	.360	9.1	28	4.9	.62	16	17	77	.74	18.9	0.062	1.6	12.0	SPR	C	Z
0.484	12.29	N-82	1.91	48.4	.424	10.8	1.2	.21	1.6	40	1.9	8.6	.33	8.4	0.030	0.8	11.0	SST	CG	N
0.484	12.29	10853	1.94	49.2	.324	8.2	59	10	.55	14	32	144	1.24	31.5	0.080	2.0	15.5	SST	CG	N
0.484	12.29	A-29	2.00	50.8	.434	11.0	.46	.08	1.7	43	.77	3.4	.33	8.3	0.025	0.6	13.0	SST	C	N
0.484	12.29	S-323	2.00	50.8	.390	9.9	5.6	.98	1.3	33	7.3	32	.71	17.9	0.047	1.2	15.0	SST	CG	N
0.484	12.29	10949	2.00	50.8	.348	8.8	30	5.3	.75	19	23	101	1.09	27.6	0.068	1.7	16.0	SPR	CG	Z
0.484	12.29	VV-29	2.00	50.8	.340	8.6	46	8.1	.55	14	26	113	1.01	25.6	0.072	1.8	14.0	HD	CG	Z
0.484	12.29	B9-68	2.06	52.4	.360	9.1	24	4.2	.72	18	17	77	.85	21.7	0.062	1.6	13.8	SPR	CG	Z
0.484	12.29	4369	2.19	55.6	.390	9.9	5.7	1.0	1.4	36	8.0	36	.79	20.0	0.047	1.2	16.8	SPR	CG	Z
0.484	12.29	11484	2.25	57.2	.400	10.2	5.8	1.0	1.0	26	5.9	26	.50	12.8	0.042	1.1	11.0	SPR	CG	Z
0.484	12.29	10417	2.25	57.2	.394	10.0	6.6	1.2	1.1	28	7.3	32	.56	14.3	0.045	1.1	12.5	SPR	CG	Z
0.484	12.29	B10-60	2.25	57.2	.384	9.8	9.5	1.7	.92	23	8.7	39	.61	15.6	0.050	1.3	12.3	SST	CG	N
0.484	12.29	10773	2.38	60.3	.452	11.5	.06	.01	2.1	53	.12	.54	.27	6.9	0.016	0.4	16.0	SST	C	N
0.484	12.29	2646	2.44	61.9	.388	9.9	9.7	1.7	1.3	32	12	54	.60	15.2	0.048	1.2	11.5	MW	C	Z
0.484	12.29	10694	2.44	61.9	.360	9.1	22	3.8	.80	20	17	77	.93	23.6	0.062	1.6	15.0	SPR	CG	GI
0.484	12.29	S-1565	2.50	63.5	.410	10.4	3.3	.59	1.1	29	3.8	17	.37	9.4	0.037	0.9				




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.500	12.70	L-4	.38	9.5	.402	10.2	90	16	.10	2.5	9.1	40	.20	5.0	0.049	1.2	3.00	SPR	C	Z
0.500	12.70	LL-83	.38	9.5	.356	9.0	493	86	.05	1.3	25	110	.29	7.3	0.072	1.8	3.00	SPR	C	Z
0.500	12.70	BB-92	.41	10.3	.432	11.0	8.3	1.4	.27	6.9	2.2	9.9	.14	3.5	0.034	0.9	4.00	SST	CG	N
0.500	12.70	10884	.44	11.1	.468	11.9	.17	.03	.31	7.9	.05	.23	.13	3.3	0.016	0.4	7.00	MW	C	Z
0.500	12.70	H-54	.44	11.1	.448	11.4	6.2	1.1	.33	8.3	2.0	9.0	.08	2.0	0.026	0.7	3.00	MW	CG	Z
0.500	12.70	S-351	.44	11.1	.422	10.7	7.5	1.3	.20	5.2	1.5	6.8	.23	5.9	0.039	1.0	6.00	SST	CG	N
0.500	12.70	3751	.44	11.1	.386	9.8	87	15	.15	3.8	13	59	.23	5.8	0.057	1.4	4.00	SPR	CG	Z
0.500	12.70	4179	.50	12.7	.462	11.7	.56	.10	.39	9.8	.22	.96	.11	2.9	0.019	0.5	5.00	MW	C	BO
0.500	12.70	S-108	.50	12.7	.460	11.7	.60	.11	.38	9.7	.23	1.0	.12	3.0	0.020	0.5	5.00	SST	C	N
0.500	12.70	2931	.50	12.7	.456	11.6	1.0	.18	.37	9.3	.38	1.7	.13	3.4	0.022	0.6	5.00	MW	C	Z
0.500	12.70	S-905	.50	12.7	.444	11.3	3.4	.60	.36	9.1	1.2	5.5	.14	3.6	0.028	0.7	4.00	SST	C	N
0.500	12.70	4118	.50	12.7	.432	11.0	19	3.3	.17	4.3	3.2	14	.14	3.5	0.034	0.9	3.00	SPR	C	Z
0.500	12.70	Y-41	.50	12.7	.430	10.9	11	1.9	.31	7.9	3.3	15	.14	3.6	0.035	0.9	4.00	SPR	CG	Z
0.500	12.70	S-118	.50	12.7	.406	10.3	33	5.7	.23	5.8	7.5	33	.19	4.8	0.047	1.2	4.00	SST	CG	N
0.500	12.70	NN-4	.50	12.7	.400	10.2	39	6.9	.23	5.8	9.0	40	.23	5.7	0.050	1.3	4.50	SPR	CG	N
0.500	12.70	B1-33	.50	12.7	.388	9.9	72	13	.16	4.2	12	52	.22	5.7	0.056	1.4	4.00	SST	CG	N
0.500	12.70	3215	.53	13.5	.460	11.7	.69	.12	.43	11	.30	1.3	.10	2.5	0.020	0.5	5.00	MW	CG	Z
0.500	12.70	G-11	.53	13.5	.398	10.1	36	6.3	.23	5.7	8.1	36	.31	7.8	0.051	1.3	5.00	SPR	C	N
0.500	12.70	O-52	.53	13.5	.310	7.9	766	134	.06	1.6	49	218	.38	9.7	0.095	2.4	4.00	SST	CG	N
0.500	12.70	L-52	.55	13.9	.300	7.6	1123	197	.05	1.4	61	271	.40	10.2	0.100	2.5	4.00	SPR	CG	Z
0.500	12.70	F-78	.56	14.3	.456	11.6	1.0	.18	.43	11	.44	2.0	.13	3.4	0.022	0.6	5.00	MW	C	Z
0.500	12.70	EE-22	.56	14.3	.420	10.7	8.2	1.4	.32	8.2	2.6	12	.24	6.1	0.040	1.0	6.00	SST	CG	N
0.500	12.70	LL-26	.56	14.3	.420	10.7	17	2.9	.30	7.5	5.0	22	.17	4.3	0.040	1.0	4.25	SPR	CG	GI
0.500	12.70	VV-37	.56	14.3	.416	10.6	23	4.1	.25	6.3	5.7	26	.21	5.3	0.042	1.1	4.00	SPR	C	GI
0.500	12.70	S-1304	.56	14.3	.392	10.0	48	8.4	.22	5.6	11	47	.24	6.2	0.054	1.4	4.50	SST	CG	N
0.500	12.70	JJ-37	.56	14.3	.380	9.7	55	9.6	.20	5.1	11	49	.36	9.1	0.060	1.5	6.00	SPR	CG	N
0.500	12.70	XX-62	.56	14.3	.316	8.0	607	106	.08	2.0	48	214	.41	10.5	0.092	2.3	4.50	SPR	CG	Z
0.500	12.70	S-1398	.56	14.3	.310	7.9	681	119	.07	1.8	49	218	.40	10.3	0.095	2.4	4.25	SST	CG	N
0.500	12.70	3611	.59	15.1	.430	10.9	11	1.9	.42	11	4.5	20	.18	4.4	0.035	0.9	4.00	MW	C	Z
0.500	12.70	12673	.59	15.1	.426	10.8	14	2.4	.40	10	5.5	24	.19	4.7	0.037	0.9	4.00	MW	C	Z
0.500	12.70	O-79	.59	15.1	.412	10.5	19	3.3	.35	8.8	6.6	29	.22	5.6	0.044	1.1	5.00	SPR	CG	Z
0.500	12.70	A14-55	.61	15.5	.420	10.7	19	3.3	.26	6.7	5.0	22	.16	4.1	0.040	1.0	4.00	SPR	CG	GI
0.500	12.70	Q-12	.63	15.9	.436	11.1	4.3	.75	.43	11	1.8	8.2	.19	4.9	0.032	0.8	5.00	SST	C	N
0.500	12.70	A14-46	.63	15.9	.424	10.8	13	2.4	.30	7.5	4.0	18	.15	3.9	0.038	1.0	4.00	SST	CG	N
0.500	12.70	PP-94	.63	15.9	.424	10.8	12	2.1	.35	8.9	4.3	19	.17	4.3	0.038	1.0	4.50	SPR	CG	GI
0.500	12.70	A11-35	.63	15.9	.422	10.7	15	2.6	.29	7.3	4.3	19	.16	4.0	0.039	1.0	4.00	SST	CG	N
0.500	12.70	AA-74	.63	15.9	.420	10.7	13	2.2	.39	9.8	4.9	22	.24	6.1	0.040	1.0	5.00	SPR	C	N
0.500	12.70	00-8	.63	15.9	.420	10.7	15	2.6	.33	8.4	5.0	22	.18	4.6	0.040	1.0	4.50	SPR	CG	N
0.500	12.70	3831	.63	15.9	.416	10.6	16	2.7	.37	9.4	5.7	26	.25	6.4	0.042	1.1	5.00	SPR	C	Z
0.500	12.70	S-1302	.63	15.9	.412	10.5	20	3.5	.31	7.9	6.2	27	.20	5.0	0.044	1.1	4.50	SST	CG	N
0.500	12.70	3905	.63	15.9	.410	10.4	31	5.5	.23	5.7	7.0	31	.18	4.6	0.045	1.1	4.00	SPR	CG	Z
0.500	12.70	A15-4	.63	15.9	.404	10.3	20	3.4	.35	8.9	6.8	30	.28	7.0	0.048	1.2	5.75	SST	CG	N
0.500	12.70	B14-37	.63	15.9	.394	10.0	45	7.9	.22	5.7	10	45	.24	6.1	0.053	1.3	4.50	SST	CG	N
0.500	12.70	10976	.63	15.9	.392	10.0	55	9.7	.20	5.2	11	50	.30	7.5	0.054	1.4	4.50	HD	C	Z
0.500	12.70	10102	.63	15.9	.376	9.6	126	22	.13	3.4	17	75	.25	6.3	0.062	1.6	4.00	HD	CG	Z
0.500	12.70	2606	.63	15.9	.370	9.4	125	22	.16	3.9	19	86	.29	7.4	0.065	1.7	4.50	SPR	CG	Z
0.500	12.70	CC-8	.63	15.9	.356	9.0	143	25	.16	4.1	23	103	.36	9.1	0.072	1.8	5.00	SST	CG	N
0.500	12.70	B-22	.66	16.7	.394	10.0	56	9.9	.19	4.8	11	47	.28	7.1	0.053	1.3	4.25	HD	C	N
0.500	12.70	S-99	.69	17.4	.410	10.4	14	2.4	.42	11	5.8	26	.27	6.9	0.045	1.1	6.00	SST	CG	N
0.500	12.70	11444	.69	17.4	.410	10.4	12	2.2	.39	10	4.9	22	.29	7.4	0.045	1.1	6.50	SST	CG	N
0.500	12.70	S-1457	.69	17.4	.408	10.4	24	4.2	.29	7.5	7.0	31	.21	5.3	0.046	1.2	4.50	SST	CG	N
0.500	12.70	3825	.69	17.4	.372	9.4	129	23	.14	3.6	19	82	.27	6.9	0.064	1.6	4.25	SPR	CG	N
0.500	12.70	LL-4	.69	17.4	.320	8.1	342	60	.13	3.4	45	201	.54	13.7	0.090	2.3	6.00	SPR	CG	GI
0.500	12.70	B5-9	.72	18.2	.424	10.8	12	2.1	.35	8.9	4.3	19	.17	4.3	0.038	1.0	4.50	SPR	CG	N
0.500	12.70	EE-78	.72	18.2	.416	10.6	21	3.6	.28	7.1	5.7	26	.18	4.5	0.042	1.1	4.25	SPR	CG	N
0.500	12.70	1881	.72	18.2	.376	9.6	101	18	.23	5.9	23	104	.28	7.1	0.062	1.6	4.50	MW	CG	Z
0.500	12.70	1932	.72	18.2	.376	9.6	84	15	.20	5.1	17	75	.37	9.4	0.062	1.6	5.00	SPR	C	Z
0.500	12.70	G-85	.72	18.2	.296	7.5	897	157	.07	1.8	64	287	.48	12.3	0.102	2.6	4.75	SPR	CG	N
0.500	12.70	B14-6	.72	18.2	.278	7.1	1236	216	.06	1.6	79	351	.56	14.1	0.11					



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.500	12.70	S-167	.81	20.6	.442	11.2	2.0	.35	.60	15	1.2	5.3	.21	5.3	0.029	0.7	6.25	SST	C	N
0.500	12.70	H-51	.81	20.6	.432	11.0	5.5	.96	.54	14	3.0	13	.20	5.2	0.034	0.9	5.00	SST	C	N
0.500	12.70	A11-33	.81	20.6	.424	10.8	9.0	1.6	.45	11	4.0	18	.19	4.8	0.038	1.0	5.00	SST	CG	N
0.500	12.70	YY-34	.81	20.6	.412	10.5	16	2.9	.37	9.5	6.2	27	.26	6.7	0.044	1.1	5.00	SST	C	N
0.500	12.70	S-1572	.81	20.6	.412	10.5	17	2.9	.37	9.3	6.2	27	.22	5.6	0.044	1.1	5.00	SST	CG	N
0.500	12.70	JJ-88	.81	20.6	.408	10.4	8.9	1.6	.41	10	3.6	16	.40	10.2	0.046	1.2	8.75	SST	CG	N
0.500	12.70	B14-29	.81	20.6	.394	10.0	42	7.4	.25	6.4	11	47	.27	6.7	0.053	1.3	5.00	SPR	CG	Z
0.500	12.70	12325	.81	20.6	.392	10.0	34	6.0	.33	8.3	11	50	.32	8.2	0.054	1.4	6.00	SPR	CG	Z
0.500	12.70	K-47	.81	20.6	.340	8.6	138	24	.23	5.8	31	140	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.500	12.70	10323	.81	20.6	.316	8.0	337	59	.14	3.6	48	214	.60	15.2	0.092	2.3	6.50	SPR	CG	Z
0.500	12.70	A15-40	.84	21.4	.432	11.0	3.7	.66	.62	16	2.3	10	.22	5.6	0.034	0.9	6.50	SST	CG	N
0.500	12.70	J-62	.84	21.4	.372	9.4	86	15	.21	5.5	19	82	.41	10.4	0.064	1.6	5.25	SPR	C	Z
0.500	12.70	10836	.88	22.2	.464	11.8	.16	.03	.69	17	.11	.49	.19	4.8	0.018	0.5	9.50	SST	C	N
0.500	12.70	B14-52	.88	22.2	.414	10.5	13	2.3	.44	11	5.8	26	.28	7.1	0.043	1.1	5.50	SST	C	N
0.500	12.70	S-1411	.88	22.2	.410	10.4	9.1	1.6	.47	12	4.3	19	.41	10.3	0.045	1.1	8.00	SST	C	N
0.500	12.70	N-135	.88	22.2	.400	10.2	25	4.3	.36	9.2	9.0	40	.30	7.6	0.050	1.3	6.00	SPR	CG	Z
0.500	12.70	S-757	.88	22.2	.390	9.9	32	5.7	.34	8.7	11	50	.39	9.8	0.055	1.4	6.00	SST	C	N
0.500	12.70	A11-40	.88	22.2	.386	9.8	44	7.6	.30	7.7	13	59	.34	8.7	0.057	1.4	6.00	SPR	CG	GI
0.500	12.70	3810	.88	22.2	.380	9.7	44	7.7	.35	8.9	15	68	.42	10.7	0.060	1.5	7.00	SPR	CG	GI
0.500	12.70	S-761	.88	22.2	.374	9.5	56	9.7	.30	7.6	17	74	.46	11.6	0.063	1.6	6.25	SST	C	N
0.500	12.70	MM-40	.88	22.2	.372	9.4	73	13	.25	6.5	19	82	.38	9.8	0.064	1.6	6.00	SPR	CG	N
0.500	12.70	L-48	.88	22.2	.340	8.6	159	28	.21	5.4	34	149	.64	16.3	0.080	2.0	7.00	SPR	CG	Z
0.500	12.70	Z-63	.88	22.2	.300	7.6	488	86	.12	2.9	57	252	.60	15.2	0.100	2.5	6.00	SST	CG	N
0.500	12.70	GG-39	.88	22.2	.280	7.1	887	155	.09	2.2	77	343	.66	16.8	0.110	2.8	6.00	SPR	CG	Z
0.500	12.70	2819	.88	22.2	.230	5.8	2455	430	.05	1.3	130	579	.81	20.6	0.135	3.4	6.00	SPR	CG	Z
0.500	12.70	A10-49	.89	22.6	.372	9.4	36	6.4	.25	6.4	9.1	40	.64	16.3	0.064	1.6	10.0	SPR	CG	Z
0.500	12.70	A9-31	.91	23.0	.460	11.7	.26	.05	.71	18	.19	.83	.20	5.1	0.020	0.5	9.00	SST	C	N
0.500	12.70	S-390	.91	23.0	.428	10.9	5.4	.94	.64	16	3.4	15	.22	5.5	0.036	0.9	6.00	SST	CG	N
0.500	12.70	S-1482	.91	23.0	.398	10.1	19	3.3	.48	12	9.0	40	.36	9.1	0.051	1.3	7.00	SST	CG	N
0.500	12.70	A15-30	.92	23.4	.420	10.7	10	1.8	.45	11	4.7	21	.21	5.3	0.040	1.0	5.25	SST	CG	N
0.500	12.70	A14-40	.94	23.8	.416	10.6	12	2.1	.46	12	5.4	24	.23	5.9	0.042	1.1	5.50	SST	CG	N
0.500	12.70	A14-61	.94	23.8	.406	10.3	21	3.6	.39	9.9	8.0	36	.27	6.8	0.047	1.2	5.75	SPR	CG	Z
0.500	12.70	S-1510	.94	23.8	.392	10.0	20	3.5	.45	11	9.0	40	.49	12.3	0.054	1.4	8.00	SST	C	N
0.500	12.70	10669	.94	23.8	.318	8.1	360	63	.13	3.3	47	208	.64	16.2	0.091	2.3	6.00	SPR	C	Z
0.500	12.70	L-31	.94	23.8	.300	7.6	372	65	.15	3.9	57	252	.73	18.4	0.100	2.5	7.25	SST	CG	N
0.500	12.70	A14-37	.97	24.6	.412	10.5	15	2.7	.44	11	6.6	29	.25	6.4	0.044	1.1	5.75	SPR	CG	N
0.500	12.70	O-38	.97	24.6	.380	9.7	24	4.2	.37	9.3	8.7	39	.60	15.2	0.060	1.5	10.0	SST	CG	N
0.500	12.70	NN-83	.97	24.6	.340	8.6	144	25	.23	5.9	34	149	.60	15.2	0.080	2.0	7.50	SPR	CG	Z
0.500	12.70	3953	1.00	25.4	.444	11.3	1.4	.25	.78	20	1.1	4.8	.22	5.7	0.028	0.7	8.00	MW	CG	Z
0.500	12.70	GG-95	1.00	25.4	.432	11.0	4.7	.83	.63	16	3.0	13	.22	5.6	0.034	0.9	5.50	SST	C	N
0.500	12.70	YY-35	1.00	25.4	.426	10.8	6.7	1.2	.55	14	3.7	16	.20	5.2	0.037	0.9	5.50	SST	CG	N
0.500	12.70	MM-89	1.00	25.4	.424	10.8	8.7	1.5	.68	17	5.9	26	.25	6.3	0.038	1.0	5.50	MW	C	N
0.500	12.70	WW-35	1.00	25.4	.424	10.8	7.6	1.3	.56	14	4.3	19	.27	6.8	0.038	1.0	6.00	SPR	C	Z
0.500	12.70	10056	1.00	25.4	.422	10.7	9.7	1.7	.48	12	4.6	21	.25	6.5	0.039	1.0	5.50	SPR	CG	GI
0.500	12.70	10326	1.00	25.4	.422	10.7	9.7	1.7	.66	17	6.4	28	.25	6.5	0.039	1.0	5.50	MW	C	GI
0.500	12.70	Z-45	1.00	25.4	.418	10.6	6.5	1.1	.61	16	3.9	18	.39	9.9	0.041	1.0	8.50	SPR	C	Z
0.500	12.70	S-755	1.00	25.4	.416	10.6	10	1.8	.53	14	5.4	24	.29	7.5	0.042	1.1	6.00	SST	C	N
0.500	12.70	A11-44	1.00	25.4	.416	10.6	13	2.3	.43	11	5.7	26	.23	5.9	0.042	1.1	5.50	SPR	CG	GI
0.500	12.70	10020	1.00	25.4	.414	10.5	15	2.6	.42	11	6.2	27	.24	6.0	0.043	1.1	5.50	SPR	CG	Z
0.500	12.70	A13-7	1.00	25.4	.408	10.4	17	3.0	.44	11	7.5	33	.28	7.0	0.046	1.2	6.00	SPR	CG	N
0.500	12.70	3635	1.00	25.4	.406	10.3	13	2.2	.62	16	7.8	35	.38	9.6	0.047	1.2	8.00	HD	CG	Z
0.500	12.70	S-1479	1.00	25.4	.406	10.3	15	2.6	.51	13	7.5	33	.35	9.0	0.047	1.2	6.50	SST	C	N
0.500	12.70	10069	1.00	25.4	.404	10.3	18	3.2	.46	12	8.5	38	.36	9.1	0.048	1.2	6.50	SPR	C	Z
0.500	12.70	Q-10	1.00	25.4	.400	10.2	22	3.8	.41	10	9.0	40	.38	9.5	0.050	1.3	6.50	SPR	C	Z
0.500	12.70	10041	1.00	25.4	.398	10.1	13	2.4	.44	11	5.9	26	.56	14.2	0.051	1.3	10.0	SPR	C	Z
0.500	12.70	2976	1.00	25.4	.392	10.0	23	4.0	.49	12	11	50	.43	11.0	0.054	1.4	8.00	SPR	CG	Z
0.500	12.70	10146	1.00	25.4	.390	9.9	31	5.5	.38	9.6	12	53	.37	9.4	0.055	1.4	6.75	SPR	CG	Z
0.500	12.70	S-758	1.00	25.4	.390	9.9	27	4.8	.41	10	11									



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./in.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.500	12.70	3748	1.13	28.6	.290	7.4	420	74	.17	4.2	70	311	.92	23.3	0.105	2.7	8.75	SPR	CG	Z
0.500	12.70	S-112	1.13	28.6	.230	5.8	1708	299	.07	1.7	117	521	.95	24.0	0.135	3.4	7.00	SST	CG	N
0.500	12.70	12650	1.14	29.0	.410	10.4	10	1.8	.68	17	7.0	31	.36	9.1	0.045	1.1	8.00	SPR	CG	N
0.500	12.70	S-328	1.16	29.4	.438	11.1		1.6	.84	21	1.3	5.9	.32	8.1	0.031	0.8	9.25	SST	C	N
0.500	12.70	S-499	1.16	29.4	.422	10.7		7.4	.59	15	4.3	19	.23	5.9	0.039	1.0	6.00	SST	CG	N
0.500	12.70	12632	1.17	29.7	.406	10.3	13	2.2	.79	20	10	44	.38	9.6	0.047	1.2	8.00	MW	CG	N
0.500	12.70	3491	1.19	30.2	.446	11.3		1.4	.97	25	1.4	6.2	.22	5.5	0.027	0.7	7.00	MW	C	Z
0.500	12.70	W-100	1.19	30.2	.430	10.9		4.1	.76	19	3.1	14	.26	6.7	0.035	0.9	6.50	SST	C	N
0.500	12.70	10774	1.19	30.2	.412	10.5	11	2.0	.58	15	6.6	29	.31	7.8	0.044	1.1	7.00	SPR	CG	Z
0.500	12.70	S-1	1.19	30.2	.406	10.3		9.6	.77	19	7.3	33	.42	10.7	0.047	1.2	9.00	SST	CG	N
0.500	12.70	S-922	1.19	30.2	.374	9.5	30	5.3	.50	13	15	66	.69	17.6	0.063	1.6	10.0	SST	C	N
0.500	12.70	FF-97	1.19	30.2	.260	6.6	836	146	.12	3.0	98	435	1.02	25.9	0.120	3.0	8.50	SPR	CG	Z
0.500	12.70	II-91	1.22	31.0	.440	11.2		1.4	.92	23	1.3	5.7	.30	7.6	0.030	0.8	10.0	MW	CG	N
0.500	12.70	LL-28	1.22	31.0	.360	9.1	47	8.2	.46	12	21	95	.72	18.2	0.070	1.8	10.3	SST	CG	N
0.500	12.70	A14-59	1.23	31.3	.420	10.7		8.7	.57	14	5.0	22	.25	6.4	0.040	1.0	6.25	SPR	CG	Z
0.500	12.70	3619	1.25	31.8	.442	11.2		.97	.87	22	.85	3.8	.38	9.6	0.029	0.7	12.0	MW	C	Z
0.500	12.70	3755	1.25	31.8	.440	11.2		3.2	.96	24	3.1	14	.20	5.0	0.030	0.8	5.50	MW	C	Z
0.500	12.70	S-756	1.25	31.8	.416	10.6		8.1	.66	17	5.4	24	.34	8.5	0.042	1.1	7.00	SST	C	N
0.500	12.70	3787	1.25	31.8	.410	10.4	13	2.2	.56	14	7.0	31	.36	9.1	0.045	1.1	7.00	SPR	C	Z
0.500	12.70	RR-70	1.25	31.8	.402	10.2		9.8	.76	19	7.5	33	.49	12.4	0.049	1.2	10.0	SST	CG	N
0.500	12.70	S-759	1.25	31.8	.390	9.9	21	3.6	.54	14	11	50	.51	12.9	0.055	1.4	8.25	SST	C	N
0.500	12.70	3512	1.25	31.8	.374	9.5	39	6.8	.62	16	24	107	.63	16.0	0.063	1.6	9.00	MW	C	Z
0.500	12.70	S-763	1.25	31.8	.374	9.5	35	6.1	.48	12	17	74	.61	15.6	0.063	1.6	8.75	SST	C	N
0.500	12.70	12197	1.25	31.8	.352	8.9	93	16	.29	7.3	27	119	.67	16.9	0.074	1.9	8.00	SPR	C	Z
0.500	12.70	EE-79	1.25	31.8	.340	8.6	93	16	.36	9.1	34	149	.84	21.3	0.080	2.0	10.5	SPR	CG	Z
0.500	12.70	Y-36	1.31	33.3	.440	11.2		1.4	1.0	26	1.4	6.3	.30	7.6	0.030	0.8	10.0	MW	CG	Z
0.500	12.70	3863	1.31	33.3	.422	10.7		5.7	.82	21	4.6	21	.35	8.9	0.039	1.0	8.00	SPR	C	Z
0.500	12.70	FF-82	1.31	33.3	.400	10.2		9.9	.66	17	6.5	29	.65	16.5	0.050	1.3	12.0	SPR	C	Z
0.500	12.70	L-62	1.31	33.3	.372	9.4	29	5.1	.54	14	16	70	.77	19.5	0.064	1.6	12.0	SPR	CG	Z
0.500	12.70	H-87	1.31	33.3	.340	8.6	77	13	.41	10	31	140	.88	22.4	0.080	2.0	11.0	SST	CG	N
0.500	12.70	1605	1.38	34.9	.454	11.5		.44	1.1	28	.48	2.2	.27	6.7	0.023	0.6	10.5	MW	C	Z
0.500	12.70	10181	1.38	34.9	.446	11.3		.90	1.1	27	.97	4.3	.30	7.5	0.027	0.7	10.0	MW	C	N
0.500	12.70	11347	1.38	34.9	.444	11.3		1.2	1.1	29	1.4	6.2	.25	6.4	0.028	0.7	8.00	SST	C	N
0.500	12.70	I-34	1.38	34.9	.436	11.1		.95	.85	22	.80	3.6	.53	13.4	0.032	0.8	15.5	SST	C	N
0.500	12.70	S-1399	1.38	34.9	.426	10.8		4.7	.78	20	3.7	16	.26	6.6	0.037	0.9	7.00	SST	C	N
0.500	12.70	A15-32	1.38	34.9	.416	10.6		7.5	.72	18	5.4	24	.36	9.1	0.042	1.1	7.50	SST	C	N
0.500	12.70	YY-29	1.38	34.9	.402	10.2		9.0	.74	19	6.7	30	.64	16.2	0.049	1.2	12.0	SPR	C	Z
0.500	12.70	XX-70	1.38	34.9	.400	10.2	12	2.2	.73	18	9.0	40	.50	12.7	0.050	1.3	10.0	SPR	CG	Z
0.500	12.70	4161	1.38	34.9	.398	10.1	13	2.4	.71	18	9.5	42	.51	13.0	0.051	1.3	10.0	SPR	CG	Z
0.500	12.70	3242	1.38	34.9	.396	10.1	12	2.0	.75	19	8.8	39	.62	15.8	0.052	1.3	12.0	SPR	CG	Z
0.500	12.70	503	1.38	34.9	.356	9.0	58	10	.43	11	25	110	.83	21.0	0.072	1.8	10.5	HD	C	Z
0.500	12.70	A15-50	1.41	35.7	.406	10.3	14	2.4	.58	15	8.0	36	.35	9.0	0.047	1.2	7.50	SPR	CG	GI
0.500	12.70	K-49	1.44	36.5	.450	11.4		.87	1.2	31	1.1	4.7	.23	5.7	0.025	0.6	8.00	MW	C	N
0.500	12.70	S-1292	1.44	36.5	.406	10.3	12	2.1	.63	16	7.5	33	.40	10.1	0.047	1.2	7.50	SST	C	N
0.500	12.70	10135	1.50	38.1	.424	10.8		5.5	.77	20	4.3	19	.32	8.2	0.038	1.0	7.50	SPR	C	Z
0.500	12.70	S-1293	1.50	38.1	.424	10.8		5.0	.79	20	4.0	18	.28	7.0	0.038	1.0	7.25	SST	CG	N
0.500	12.70	11745	1.50	38.1	.424	10.8		6.1	.70	18	4.3	19	.27	6.8	0.038	1.0	7.00	SPR	CG	Z
0.500	12.70	3878	1.50	38.1	.420	10.7		7.6	.66	17	5.0	22	.32	8.1	0.040	1.0	7.00	SPR	C	Z
0.500	12.70	521	1.50	38.1	.418	10.6		5.3	1.0	26	5.4	24	.45	11.5	0.041	1.0	10.0	HD	C	Z
0.500	12.70	B6-1	1.50	38.1	.418	10.6		6.8	1.2	19	5.0	22	.35	8.9	0.041	1.0	7.50	SST	C	N
0.500	12.70	S-1290	1.50	38.1	.418	10.6		6.4	.79	20	5.0	22	.32	8.1	0.041	1.0	7.75	SST	CG	N
0.500	12.70	S-1296	1.50	38.1	.418	10.6		4.1	1.0	27	4.3	19	.45	11.5	0.041	1.0	11.0	SST	CG	N
0.500	12.70	S-806	1.50	38.1	.418	10.6		4.1	1.0	27	4.3	19	.45	11.5	0.041	1.0	11.0	SST	CG	N
0.500	12.70	10081	1.50	38.1	.418	10.6		7.3	.73	19	5.4	24	.32	8.1	0.041	1.0	7.75	SPR	CG	GI
0.500	12.70	S-122	1.50	38.1	.406	10.3		8.2	.91	23	7.5	33	.47	11.9	0.047	1.2	10.0	SST	CG	N
0.500	12.70	S-247	1.50	38.1	.396	10.1	14	2.4	.70	18	9.5	42	.49	12.5	0.052	1.3	9.50	SST	CG	N
0.500	12.70	11421	1.50	38.1	.396	10.1	11	1.9	.85	22	9.5	42	.65	16.5	0.052	1.3	12.5	HD	CG	Z
0.500	12.70	S-243	1.50	38.1	.392	10.0	17	3.0	.62	16	11	47	.49	12.3	0.054	1.4	9.00	SST	CG	N
0.500	12.70	10059	1.50	38.1	.390	9.9	2													



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.500	12.70	11159	1.66	42.1	.330	8.4	100	18	.40	10	40	178	1.06	27.0	0.085	2.2	12.5	SPR	CG	Z
0.500	12.70	B14-55	1.69	42.8	.410	10.4	6.3	1.1	1.1	29	7.0	31	.54	13.7	0.045	1.1	12.0	SPR	CG	N
0.500	12.70	A10-58	1.72	43.6	.394	10.0	13	2.2	.84	21	11	47	.64	16.2	0.053	1.3	12.0	SPR	CG	N
0.500	12.70	QQ-58	1.75	44.5	.420	10.7	3.4	.60	1.2	30	4.1	18	.56	14.2	0.040	1.0	13.0	MW	C	Z
0.500	12.70	511	1.75	44.5	.376	9.6	24	4.1	.72	18	17	75	.85	21.7	0.062	1.6	12.8	HD	C	Z
0.500	12.70	JJ-89	1.75	44.5	.368	9.3	34	6.0	.59	15	20	90	.84	21.4	0.066	1.7	11.8	SPR	C	N
0.500	12.70	359	1.75	44.5	.356	9.0	43	7.6	.57	14	25	110	1.03	26.2	0.072	1.8	13.3	HD	C	Z
0.500	12.70	11582	1.75	44.5	.354	9.0	48	8.3	.54	14	26	115	1.02	26.0	0.073	1.9	13.0	SPR	CG	N
0.500	12.70	10311	1.81	46.0	.384	9.8	13	2.2	.84	21	11	48	.97	24.7	0.058	1.5	16.8	SPR	CG	Z
0.500	12.70	K-99	1.81	46.0	.356	9.0	35	6.2	.66	17	23	103	1.15	29.3	0.072	1.8	16.0	SPR	CG	GI
0.500	12.70	B14-69	1.84	46.8	.322	8.2	144	25	.32	8.0	46	203	.98	24.9	0.089	2.3	11.0	SPR	CG	Z
0.500	12.70	QQ-53	1.88	47.6	.406	10.3	6.3	1.1	1.2	30	7.4	33	.71	17.9	0.047	1.2	14.0	HD	C	Z
0.500	12.70	3580	1.88	47.6	.396	10.1	8.9	1.6	1.1	28	9.7	43	.79	20.0	0.052	1.3	15.0	HD	CG	Z
0.500	12.70	A12-40	1.88	47.6	.394	10.0	11	1.8	.95	24	10	45	.66	16.8	0.053	1.3	12.5	SST	CG	N
0.500	12.70	3608	1.88	47.6	.392	10.0	9.2	1.6	.90	23	8.3	37	.97	24.7	0.054	1.4	17.0	SPR	C	Z
0.500	12.70	10384	1.88	47.6	.380	9.7	15	2.6	.80	20	12	52	1.08	27.4	0.060	1.5	17.0	SPR	C	Z
0.500	12.70	11772	1.91	48.4	.440	11.2	1.4	.25	1.6	41	2.3	10	.30	7.6	0.030	0.8	10.0	MW	CG	GI
0.500	12.70	10603	1.91	48.4	.392	10.0	14	2.4	.82	21	11	50	.65	16.5	0.054	1.4	12.0	SPR	CG	Z
0.500	12.70	12317	1.91	48.4	.374	9.5	32	5.6	.55	14	18	79	.72	18.4	0.063	1.6	10.5	SPR	C	Z
0.500	12.70	12724	1.92	48.8	.438	11.1	1.6	.28	1.6	41	2.6	12	.31	7.9	0.031	0.8	10.0	MW	CG	GI
0.500	12.70	4232	1.94	49.2	.356	9.0	55	9.6	.45	11	25	110	.86	21.9	0.072	1.8	11.0	SPR	C	Z
0.500	12.70	K-53	1.97	50.0	.406	10.3	5.6	.98	1.2	31	6.9	31	.73	18.5	0.047	1.2	15.5	SPR	CG	Z
0.500	12.70	FF-55	2.00	50.8	.424	10.8	2.6	.46	1.5	38	4.0	18	.49	12.5	0.038	1.0	12.0	SST	C	N
0.500	12.70	B10-63	2.00	50.8	.420	10.7	4.7	.83	1.1	27	5.0	22	.44	11.2	0.040	1.0	10.0	SPR	C	Z
0.500	12.70	3994	2.00	50.8	.418	10.6	3.0	.53	1.3	33	3.9	17	.70	17.7	0.041	1.0	16.0	SPR	C	Z
0.500	12.70	O-95	2.00	50.8	.408	10.4	5.1	.89	1.3	33	6.6	29	.71	18.1	0.046	1.2	15.5	SPR	CG	Z
0.500	12.70	15	2.00	50.8	.406	10.3	7.2	1.3	1.1	28	8.0	36	.64	16.1	0.047	1.2	12.5	HD	C	Z
0.500	12.70	2721	2.00	50.8	.406	10.3	5.8	1.0	1.2	32	7.2	32	.75	19.1	0.047	1.2	15.0	HD	C	Z
0.500	12.70	AA-87	2.00	50.8	.400	10.2	5.9	1.0	1.2	30	6.9	31	.83	21.0	0.050	1.3	16.5	SST	CG	N
0.500	12.70	12233	2.00	50.8	.388	9.9	13	2.3	.97	25	13	56	.81	20.6	0.056	1.4	14.5	SPR	CG	GI
0.500	12.70	3004	2.00	50.8	.376	9.6	24	4.2	.70	18	17	75	.78	19.7	0.062	1.6	12.5	SPR	CG	Z
0.500	12.70	S-765	2.00	50.8	.374	9.5	21	3.6	.81	21	17	74	.91	23.2	0.063	1.6	13.5	SST	C	N
0.500	12.70	4215	2.00	50.8	.372	9.4	34	6.0	.54	14	19	82	.74	18.7	0.064	1.6	10.5	SPR	C	Z
0.500	12.70	504	2.00	50.8	.356	9.0	38	6.6	.65	17	25	110	1.15	29.3	0.072	1.8	15.0	HD	C	Z
0.500	12.70	2652	2.03	51.6	.462	11.7	.14	.02	1.7	44	.24	1.1	.29	7.4	0.019	0.5	14.3	MW	C	Z
0.500	12.70	3160	2.03	51.6	.362	9.2	28	4.9	.82	21	23	103	1.14	28.9	0.069	1.8	16.5	SPR	CG	Z
0.500	12.70	12684	2.06	52.4	.330	8.4	91	16	.61	16	56	249	1.15	29.2	0.085	2.2	13.5	MW	CG	Z
0.500	12.70	S-39	2.13	54.0	.406	10.3	3.1	.53	1.0	26	3.1	14	1.10	28.1	0.047	1.2	23.5	SST	CG	N
0.500	12.70	3558	2.13	54.0	.402	10.2	11	2.0	1.1	28	13	56	.49	12.4	0.049	1.2	10.0	MW	CG	Z
0.500	12.70	Q-61-A	2.13	54.0	.388	9.9	10	1.8	1.1	29	12	52	.87	22.0	0.056	1.4	15.5	SST	CG	N
0.500	12.70	10033	2.19	55.6	.312	7.9	124	22	.41	10	51	228	1.46	37.0	0.094	2.4	15.5	SPR	CG	Z
0.500	12.70	YY-62	2.25	57.2	.460	11.7	.23	.04	2.0	52	.46	2.0	.22	5.6	0.020	0.5	10.0	SST	C	N
0.500	12.70	4322	2.25	57.2	.340	8.6	69	12	.49	12	34	149	1.08	27.4	0.080	2.0	13.5	SPR	CG	Z
0.500	12.70	12020	2.31	58.7	.398	10.1	13	2.4	.71	18	9.5	42	.51	13.0	0.051	1.3	10.0	SPR	CG	Z
0.500	12.70	3776	2.31	58.7	.356	9.0	32	5.6	.78	20	25	110	1.26	32.0	0.072	1.8	17.5	HD	CG	GI
0.500	12.70	J-34	2.31	58.7	.356	9.0	58	10	.43	11	25	110	.76	19.2	0.072	1.8	10.5	HD	CG	Z
0.500	12.70	3159	2.38	60.3	.372	9.4	20	3.6	.91	23	19	82	1.04	26.4	0.064	1.6	16.3	SPR	CG	Z
0.500	12.70	10042	2.38	60.3	.366	9.3	34	6.0	.62	16	21	94	.90	23.0	0.067	1.7	12.5	SPR	C	Z
0.500	12.70	4266	2.44	61.9	.376	9.6	17	3.0	.98	25	17	75	1.04	26.4	0.062	1.6	16.8	SPR	CG	Z
0.500	12.70	12599	2.50	63.5	.424	10.8	3.0	.53	1.9	49	5.9	26	.49	12.5	0.038	1.0	12.0	MW	C	Z
0.500	12.70	EE-59	2.50	63.5	.400	10.2	13	2.3	.68	17	9.0	40	.48	12.1	0.050	1.3	9.50	SPR	CG	N
0.500	12.70	24	2.50	63.5	.376	9.6	16	2.8	1.1	27	17	75	1.18	29.9	0.062	1.6	18.0	HD	C	Z
0.500	12.70	3035	2.50	63.5	.376	9.6	21	3.7	.80	20	17	75	.87	22.0	0.062	1.6	14.0	SPR	CG	Z
0.500	12.70	S-1133	2.50	63.5	.376	9.6	13	2.3	1.2	31	16	71	1.24	31.5	0.062	1.6	19.0	SST	C	N
0.500	12.70	11928	2.50	63.5	.356	9.0	38	6.6	.65	17	25	110	1.08	27.4	0.072	1.8	15.0	SPR	CG	Z
0.500	12.70	12287	2.53	64.3	.376	9.6	17	3.0	1.0	25	17	75	1.12	28.3	0.062	1.6	17.0	SPR	C	Z
0.500	12.70	12302	2.59	65.9	.424	10.8	2.1	.37	2.0	50	4.1	18	.63	15.9	0.038	1.0	16.5	SP		



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com


O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.500	12.70	12139	4.19	106.4	.424	10.8	1.4	.25	3.0	75	4.3	19	.87	22.2	0.038	1.0	23.0	SPR	CG	Z
0.500	12.70	3476	4.50	114.3	.356	9.0	29	5.1	.85	22	25	110	1.44	36.6	0.072	1.8	19.0	HD	C	Z
0.500	12.70	11651	4.75	120.7	.408	10.4	1.8	.32	2.9	74	5.3	23	1.84	46.7	0.046	1.2	40.0	SPR	CG	Z
0.500	12.70	K-37	4.75	120.7	.318	8.1	40	7.0	1.2	30	47	208	3.46	87.8	0.091	2.3	38.0	SPR	CG	GI
0.500	12.70	12690	5.50	139.7	.406	10.3	2.4	.43	3.3	84	8.0	36	1.60	40.6	0.047	1.2	33.0	HD	C	BO
0.500	12.70	B15-55	5.50	139.7	.406	10.3	2.6	.46	3.1	78	8.0	36	1.46	37.0	0.047	1.2	31.0	SPR	CG	Z
0.500	12.70	3251	5.50	139.7	.364	9.2	8.9	1.6	2.4	62	22	96	3.06	77.7	0.068	1.7	45.0	SPR	CG	Z
0.500	12.70	12218	5.94	150.8	.336	8.5	42	7.4	.85	22	36	160	1.89	47.9	0.082	2.1	23.0	SPR	CG	Z
0.500	12.70	S-1277	6.50	165.1	.392	10.0	3.2	.55	3.4	85	11	47	2.16	54.9	0.054	1.4	40.0	SST	CG	N
0.500	12.70	12688	9.00	228.6	.376	9.6	4.2	.74	4.0	102	17	75	3.91	99.2	0.062	1.6	62.0	SPR	C	Z
0.500	12.70	3998	10.5	266.7	.356	9.0	7.4	1.3	3.3	85	25	110	4.93	125.3	0.072	1.8	68.5	SPR	CG	Z
0.500	12.70	880	12.0	304.8	.376	9.6	3.1	.54	5.4	138	17	75	5.24	133.1	0.062	1.6	83.5	HD	C	Z
0.500	12.70	886	12.0	304.8	.340	8.6	9.0	1.6	3.8	95	34	149	7.34	186.4	0.080	2.0	90.8	HD	C	Z
0.500	12.70	3155	14.0	355.6	.392	10.0	1.9	.34	5.9	149	11	50	4.03	102.4	0.054	1.4	74.0	SPR	C	Z
0.500	12.70	514	16.0	406.4	.392	10.0	1.4	.24	8.2	209	11	50	5.59	142.0	0.054	1.4	102.0	HD	C	Z
0.515	13.08	V-21	.50	12.7	.371	9.4	296	52	.08	2.1	24	107	.25	6.4	0.072	1.8	3.50	SPR	CG	GI
0.515	13.08	O-115	.56	14.3	.437	11.1	8.9	1.6	.33	8.3	2.9	13	.23	5.9	0.039	1.0	5.00	SST	C	N
0.515	13.08	A14-4	.56	14.3	.401	10.2	74	13	.17	4.4	13	57	.24	6.0	0.057	1.4	4.13	SPR	CG	GI
0.515	13.08	B15-16	.56	14.3	.355	9.0	318	56	.10	2.6	33	146	.34	8.6	0.080	2.0	4.25	SPR	CG	N
0.515	13.08	B15-65	.63	15.9	.481	12.2	.78	.14	.55	14	.43	1.9	.07	1.8	0.017	0.4	3.25	MW	C	Z
0.515	13.08	B2-41	.63	15.9	.443	11.3	2.4	.42	.27	6.7	.63	2.8	.36	9.1	0.036	0.9	10.0	SST	CG	N
0.515	13.08	3258	.63	15.9	.345	8.8	629	110	.06	1.6	39	173	.38	9.7	0.085	2.2	3.50	SPR	C	Z
0.515	13.08	2657	.69	17.4	.345	8.8	290	51	.13	3.4	39	173	.45	11.3	0.085	2.2	5.25	SPR	CG	Z
0.515	13.08	3136	.75	19.1	.407	10.3	36	6.2	.31	7.8	11	49	.30	7.5	0.054	1.4	5.50	SPR	CG	Z
0.515	13.08	W-37	.75	19.1	.407	10.3	25	4.4	.37	9.4	9.3	41	.38	9.6	0.054	1.4	7.00	SPR	CG	Z
0.515	13.08	2640	.78	19.8	.391	9.9	87	15	.26	6.7	23	101	.29	7.3	0.062	1.6	4.75	MW	CG	Z
0.515	13.08	A15-70	.81	20.6	.411	10.4	19	3.3	.45	11	8.4	37	.36	9.2	0.052	1.3	7.00	SST	CG	N
0.515	13.08	3389	.81	20.6	.391	9.9	57	10	.29	7.3	16	73	.37	9.4	0.062	1.6	6.00	SPR	CG	Z
0.515	13.08	DD-96	.81	20.6	.355	9.0	131	23	.23	5.9	31	136	.54	13.7	0.080	2.0	6.75	SST	CG	N
0.515	13.08	FF-20	.88	22.2	.455	11.6	3.1	.55	.69	17	2.2	9.6	.19	4.8	0.030	0.8	5.25	MW	C	Z
0.515	13.08	Y-23	.88	22.2	.415	10.5	22	3.9	.39	9.9	8.7	39	.30	7.6	0.050	1.3	6.00	SPR	CG	N
0.515	13.08	S-1060	.88	22.2	.405	10.3	20	3.4	.44	11	8.5	38	.44	11.2	0.055	1.4	8.00	SST	CG	N
0.515	13.08	3841	.94	23.8	.331	8.4	272	48	.17	4.4	47	209	.64	16.4	0.092	2.3	7.00	HD	CG	GI
0.515	13.08	00-79	.97	24.6	.435	11.0	4.6	.80	.63	16	2.9	13	.34	8.6	0.040	1.0	8.50	SST	CG	N
0.515	13.08	KK-48	1.00	25.4	.455	11.6	3.4	.60	.85	22	2.9	13	.15	3.8	0.030	0.8	5.00	MW	CG	N
0.515	13.08	B3-36	1.00	25.4	.443	11.3	6.8	1.2	.72	18	4.9	22	.23	5.7	0.036	0.9	5.25	MW	C	N
0.515	13.08	K-29	1.00	25.4	.419	10.6	10	1.8	.60	15	6.3	28	.40	10.1	0.048	1.2	8.25	SST	CG	N
0.515	13.08	VW-43	1.00	25.4	.379	9.6	63	11	.34	8.7	22	96	.58	14.7	0.068	1.7	7.50	SPR	C	Z
0.515	13.08	S-1171	1.00	25.4	.355	9.0	124	22	.25	6.3	31	136	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.515	13.08	Y-30	1.06	27.0	.453	11.5	2.0	.34	.81	21	1.6	7.1	.25	6.3	0.031	0.8	8.00	MW	CG	Z
0.515	13.08	10838	1.06	27.0	.447	11.4	2.4	.42	.75	19	1.8	7.9	.32	8.0	0.034	0.9	9.25	SPR	CG	Z
0.515	13.08	12481	1.06	27.0	.425	10.8	7.6	1.3	.59	15	4.5	20	.47	12.0	0.045	1.1	9.50	MW	C	N
0.515	13.08	11107	1.13	28.6	.457	11.6	1.5	.26	.86	22	1.3	5.7	.26	6.6	0.029	0.7	8.00	MW	C	Z
0.515	13.08	S-235	1.13	28.6	.453	11.5	1.4	.25	.81	21	1.1	5.0	.32	8.1	0.031	0.8	9.25	SST	C	N
0.515	13.08	2715	1.13	28.6	.387	9.8	48	8.4	.52	13	25	111	.48	12.2	0.064	1.6	7.50	MW	CG	Z
0.515	13.08	S-1051	1.13	28.6	.305	7.7	367	64	.17	4.4	63	282	.84	21.3	0.105	2.7	8.00	SST	CG	N
0.515	13.08	B10-64	1.16	29.4	.379	9.6	53	9.3	.41	10	22	96	.58	14.7	0.068	1.7	8.50	SPR	CG	Z
0.515	13.08	S-1613	1.19	30.2	.407	10.3	14	2.4	.65	16	9.0	40	.54	13.7	0.054	1.4	10.0	SST	CG	N
0.515	13.08	11338	1.19	30.2	.341	8.7	175	31	.24	6.0	42	185	.78	19.9	0.087	2.2	8.00	SPR	C	Z
0.515	13.08	S-1032	1.25	31.8	.459	11.7	.42	.07	.75	19	.31	1.4	.50	12.8	0.028	0.7	18.0	SST	CG	N
0.515	13.08	3972	1.25	31.8	.391	9.9	48	8.4	.34	8.7	16	73	.42	10.6	0.062	1.6	6.75	SPR	CG	Z
0.515	13.08	10460	1.30	32.9	.397	10.1	27	4.8	.49	12	13	59	.47	12.0	0.059	1.5	8.00	SST	CG	N
0.515	13.08	2526	1.38	34.9	.427	10.8	9.4	1.6	.68	17	6.4	29	.37	9.5	0.044	1.1	7.50	SPR	C	Z
0.515	13.08	3535	1.41	35.7	.421	10.7	12	2.2	.87	22	11	48	.35	9.0	0.047	1.2	7.50	MW	CG	Z
0.515	13.08	10809	1.50	38.1	.485	12.3	.08	.01	1.4	34	.11	50	.15	3.8	0.015	0.4	9.00	MW	C	N
0.515	13.08	2560	1.50	38.1	.451	11.5	1.7	.29	1.2	30	2.0	8.8	.32	8.1	0.032	0.8	10.0	HD	CG	Z
0.515	13.08	Z-24	1.50	38.1	.451	11.5	2.7	.47	.98	25	2.6	12	.26	6.5	0.032	0.8	7.00	SPR	C	Z
0.515	13.08	10718	1.50	38.1	.433	11.0	5.7	.99	.92	23	5.2	23	.40	10.2	0.041	1.0	8.75			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.515	13.08	S-278	2.50	63.5	.411	10.4	6.1	1.1	1.5	38	9.2	41	.94	23.8	0.052	1.3	17.0	SST	C	N
0.515	13.08	3429	2.63	66.7	.265	6.7	438	77	.24	6.2	107	476	1.94	49.2	0.125	3.2	15.5	SPR	CG	Z
0.515	13.08	A13-37	2.66	67.5	.369	9.4	25	4.3	.95	24	24	105	1.46	37.1	0.073	1.9	19.0	SST	C	N
0.515	13.08	11635	2.69	68.2	.415	10.5	5.6	.98	1.6	40	8.7	39	.90	22.9	0.050	1.3	18.0	SPR	CG	Z
0.515	13.08	3838	2.69	68.2	.387	9.8	11	2.0	1.1	28	12	55	1.60	40.6	0.064	1.6	25.0	SPR	CG	Z
0.515	13.08	2558	2.69	68.2	.265	6.7	382	67	.39	9.9	150	665	2.19	55.6	0.125	3.2	17.5	MW	CG	Z
0.515	13.08	3140	2.75	69.9	.437	11.1	4.2	.74	1.1	27	4.5	20	.40	10.2	0.039	1.0	9.25	SPR	C	Z
0.515	13.08	12300	3.00	76.2	.395	10.0	11	1.9	1.4	34	15	66	1.20	30.5	0.060	1.5	20.0	SPR	CG	Z
0.515	13.08	2510	3.25	82.6	.399	10.1	12	2.1	1.6	41	19	83	.96	24.3	0.058	1.5	16.5	MW	CG	Z
0.515	13.08	B-26	3.28	83.3	.433	11.0	3.8	.67	1.4	35	5.2	23	.53	13.5	0.041	1.0	12.0	HD	C	N
0.515	13.08	11557	3.59	91.3	.387	9.8	12	2.1	1.5	38	18	80	1.60	40.6	0.064	1.6	24.0	SPR	CG	N
0.515	13.08	10928	4.00	101.6	.347	8.8	40	7.0	.95	24	38	168	2.14	54.4	0.084	2.1	24.5	SPR	C	Z
0.515	13.08	10705	5.31	134.9	.315	8.0	54	9.5	1.1	28	60	265	3.90	99.1	0.100	2.5	39.0	SPR	CG	Z
0.515	13.08	11517	5.50	139.7	.421	10.7	2.4	.41	3.3	84	7.8	35	1.50	38.2	0.047	1.2	31.0	SPR	CG	Z
0.515	13.08	12298	6.00	152.4	.421	10.7	3.6	.63	2.2	55	7.8	35	.99	25.1	0.047	1.2	21.0	SPR	CG	Z
0.515	13.08	11431	7.63	193.7	.411	10.4	1.8	.31	4.3	110	7.6	34	3.30	83.9	0.052	1.3	62.5	HD	C	Z
0.515	13.08	1609	8.50	215.9	.391	9.9	5.3	.93	3.1	78	16	73	2.79	70.9	0.062	1.6	45.0	SPR	CG	Z
0.515	13.08	S-188	8.75	222.3	.391	9.9	4.6	.81	3.3	85	15	69	2.79	70.9	0.062	1.6	45.0	SST	CG	N
0.515	13.08	1809	12.0	304.8	.391	9.9	2.9	.51	7.0	177	20	91	5.02	127.6	0.062	1.6	80.0	MW	C	Z
0.531	13.49	N-81	.28	7.1	.437	11.1	62	11	.12	3.1	7.6	34	.14	3.6	0.047	1.2	3.00	SPR	CG	N
0.531	13.49	3050	.31	7.9	.467	11.9	12	2.1	.21	5.3	2.5	11	.10	2.4	0.032	0.8	3.00	SPR	CG	Z
0.531	13.49	2851	.44	11.1	.485	12.3	1.5	.27	.32	8.2	.50	2.2	.12	2.9	0.023	0.6	4.00	MW	C	Z
0.531	13.49	B10-36	.44	11.1	.441	11.2	19	3.3	.22	5.7	4.2	19	.21	5.4	0.045	1.1	4.75	SPR	CG	Z
0.531	13.49	I-14	.50	12.7	.441	11.2	30	5.2	.21	5.3	6.2	28	.16	4.0	0.045	1.1	3.50	SST	CG	N
0.531	13.49	S-17	.50	12.7	.437	11.1	27	4.7	.26	6.7	7.1	32	.19	4.8	0.047	1.2	4.00	SST	CG	N
0.531	13.49	PP-32	.56	14.3	.387	9.8	107	19	.15	3.8	16	70	.41	10.5	0.072	1.8	5.75	SPR	CG	Z
0.531	13.49	G-57	.56	14.3	.371	9.4	186	33	.16	4.1	30	133	.40	10.2	0.080	2.0	5.00	SST	CG	N
0.531	13.49	S-823	.63	15.9	.481	12.2	.75	.13	.43	11	.32	1.4	.20	5.1	0.025	0.6	7.00	SST	C	N
0.531	13.49	2670	.63	15.9	.465	11.8	6.9	1.2	.40	10	2.8	12	.17	4.2	0.033	0.8	4.00	SPR	C	Z
0.531	13.49	M-131	.63	15.9	.459	11.7	5.9	1.0	.45	11	2.6	12	.18	4.6	0.036	0.9	5.00	SST	CG	N
0.531	13.49	L-35	.63	15.9	.407	10.3	73	13	.21	5.2	15	67	.28	7.1	0.062	1.6	4.50	SST	CG	N
0.531	13.49	F-54	.66	16.7	.405	10.3	88	15	.19	4.8	17	74	.28	7.2	0.063	1.6	4.50	HD	CG	Z
0.531	13.49	YY-58	.69	17.4	.463	11.8	7.8	1.4	.39	9.9	3.0	13	.17	4.3	0.034	0.9	4.00	SPR	C	GI
0.531	13.49	N-132	.69	17.4	.407	10.3	69	12	.23	5.9	16	71	.31	7.9	0.062	1.6	5.00	SPR	CG	Z
0.531	13.49	3906	.72	18.2	.451	11.5	7.8	1.4	.44	11	3.4	15	.28	7.1	0.040	1.0	6.00	SPR	C	Z
0.531	13.49	CC-53	.75	19.1	.467	11.9	4.0	.71	.56	14	2.3	10	.19	4.9	0.032	0.8	5.00	MW	C	Z
0.531	13.49	2586	.75	19.1	.449	11.4	14	2.4	.51	13	7.0	31	.18	4.7	0.041	1.0	4.50	MW	CG	Z
0.531	13.49	4269	.75	19.1	.437	11.1	15	2.7	.42	11	6.5	29	.33	8.4	0.047	1.2	6.00	SPR	C	Z
0.531	13.49	B11-51	.75	19.1	.403	10.2	53	9.2	.31	8.0	16	73	.38	9.8	0.064	1.6	6.00	SST	CG	N
0.531	13.49	10260	.75	19.1	.349	8.9	386	68	.11	2.9	44	197	.46	11.6	0.091	2.3	5.00	SPR	CG	Z
0.531	13.49	1953	.78	19.8	.487	12.4	.68	.12	.63	16	.43	1.9	.15	3.8	0.022	0.6	5.75	MW	C	Z
0.531	13.49	S-919	.78	19.8	.387	9.8	99	17	.22	5.6	22	98	.40	10.1	0.072	1.8	5.50	SST	CG	N
0.531	13.49	2592	.78	19.8	.321	8.2	646	113	.10	2.6	67	296	.58	14.7	0.105	2.7	5.50	SPR	CG	Z
0.531	13.49	B11-37	.81	20.6	.467	11.9	4.0	.71	.63	16	2.5	11	.16	4.1	0.032	0.8	5.00	SPR	CG	N
0.531	13.49	S-446	.81	20.6	.407	10.3	72	13	.21	5.3	15	67	.28	7.1	0.062	1.6	4.50	SST	CG	N
0.531	13.49	2787	.81	20.6	.345	8.8	320	56	.15	3.7	47	210	.56	14.2	0.093	2.4	6.00	SPR	CG	Z
0.531	13.49	2559	.84	21.4	.423	10.7	23	3.9	.47	12	10	47	.38	9.6	0.054	1.4	7.00	HD	CG	Z
0.531	13.49	V-29	.84	21.4	.407	10.3	45	7.8	.34	8.5	15	67	.37	9.4	0.062	1.6	6.00	SST	CG	N
0.531	13.49	S-895	.88	22.2	.467	11.9	3.5	.62	.67	17	2.4	10	.16	4.1	0.032	0.8	5.00	SST	CG	N
0.531	13.49	10734	.88	22.2	.449	11.4	8.6	1.5	.59	15	5.1	22	.25	6.2	0.041	1.0	6.00	SPR	CG	Z
0.531	13.49	3836	.88	22.2	.427	10.8	32	5.6	.30	7.6	9.5	42	.31	7.9	0.052	1.3	5.00	SPR	C	Z
0.531	13.49	2636	.91	23.0	.417	10.6	28	5.0	.44	11	12	55	.40	10.1	0.057	1.4	7.00	HD	CG	Z
0.531	13.49	JJ-17	.94	23.8	.471	12.0	1.9	.32	.70	18	1.3	5.7	.24	6.1	0.030	0.8	7.00	MW	C	Z
0.531	13.49	S-1412	.94	23.8	.449	11.4	8.6	1.5	.55	14	4.7	21	.23	5.7	0.041	1.0	5.50	SST	CG	N
0.531	13.49	2896	.94	23.8	.429	10.9	22	3.8	.41	10	9.0	40	.36	9.1	0.051	1.3	6.00	SPR	C	Z
0.531	13.49	I-47	.94	23.8	.407	10.3	21	3.6	.19	4.9	4.0	18	.74	18.9	0.062	1.6	12.0	HD	CG	N
0.531	13.49	A12-12	1.00	25.4	.471	12.0	1.6	.28	.74	19	1.2	5.3	.26	6.7	0.030	0.8	7.75	MW	C	N
0.531	13.49	A12-30	1.00	25.4	.471	12.0	1.5	.27	.73	19	1.1	5.0	.27	6.9	0.030	0.8	8.00	MW	C	Z
0.531	13.49	11204	1.00	25.4	.467	11.9	1.7	.30	.70	18	1.2	5.4	.30	7.5	0.032	0.8	8.25	SST	C	N
0.531	13.49	S-81	1.00	25.4	.443	11.3	10	1.8	.57	15	5.8	26	.31	7.8	0.044	1.1	6.00	SST	C	N
0.531	13.49	11208	1.00	25.4	.407	10.3	33	5.8	.45	11	15	67	.47	11.8	0.062	1.6	7.50	SST	CG	N
0.531	13.49	S-916	1.00	25.4	.405	10.3	64	11	.25	6.2	16	70	.32	8.0	0.063	1.6	5.00	SST	CG	N
0.531	13.49	10034	1.00	25.4	.381	9.7	120	21	.22	5.6	26	117	.45	11.4	0.075	1.9	6.00	SPR	CG	Z
0.531	13.49	11200	1.03	26.2	.469	11.9	1.6	.27	.75	19	1.2	5.3	.28	7.1	0.031	0.8	8.00	SST	C	N
0.531	13.49	B10-39	1.03	26.2	.441	11.2	8.9	1.6	.68	17	6.1	27	.35	8.9	0.045	1.1	7.75	SPR	CG	N
0.531	13.49	12401	1.03	26.2	.321	8.2	432	76	.15	3.9	67	296	.73	18.5	0.105	2.7	7.00	SPR	CG	N
0.531	13.49	12497	1.06	27.0	.473	12.0	1.4	.24	.81	21	1.1	5.0	.25	6.5	0.029	0.7	7.75	MW	C	N
0.531	13.49	10691	1.06	27.0	.463	11.8	2.0	.34	.72	18	1.4	6.3	.34	8.6	0.034	0.9	10.0	SPR	CG	Z



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E F I D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.540	13.72	71686S	.63	16.0	.414	10.5	67	12	.23	5.9	15	69	.29	7.4	0.063	1.6	4.63	SST	CG	N
0.540	13.72	71699	.63	16.0	.406	10.3	102	18	.27	6.8	27	122	.31	7.9	0.067	1.7	4.63	MW	CG	N
0.540	13.72	71699S	.63	16.0	.406	10.3	87	15	.21	5.4	19	83	.31	7.9	0.067	1.7	4.63	SST	CG	N
0.540	13.72	71635	.75	19.1	.458	11.6	13	2.3	.52	13	6.9	31	.18	4.7	0.041	1.0	4.50	MW	CG	N
0.540	13.72	71635S	.75	19.1	.458	11.6	11	2.0	.41	10	4.7	21	.18	4.7	0.041	1.0	4.50	SST	CG	N
0.540	13.72	71648	.75	19.1	.448	11.4	20	3.4	.50	13	9.7	43	.22	5.5	0.046	1.2	4.75	MW	CG	N
0.540	13.72	71648S	.75	19.1	.448	11.4	17	2.9	.39	10	6.5	29	.22	5.5	0.046	1.2	4.75	SST	CG	N
0.540	13.72	71661	.75	19.1	.432	11.0	35	6.1	.42	11	15	65	.27	6.9	0.054	1.4	5.00	MW	CG	N
0.540	13.72	71661S	.75	19.1	.432	11.0	30	5.2	.33	8.4	9.8	44	.27	6.9	0.054	1.4	5.00	SST	CG	N
0.540	13.72	71674	.75	19.1	.424	10.8	46	8.0	.39	9.9	18	80	.30	7.6	0.058	1.5	5.13	MW	CG	N
0.540	13.72	71674S	.75	19.1	.424	10.8	39	6.8	.31	7.9	12	54	.30	7.6	0.058	1.5	5.13	SST	CG	N
0.540	13.72	71687	.75	19.1	.414	10.5	63	11	.36	9.2	23	102	.33	8.4	0.063	1.6	5.25	MW	CG	N
0.540	13.72	71687S	.75	19.1	.414	10.5	54	9.4	.29	7.3	15	69	.33	8.4	0.063	1.6	5.25	SST	CG	N
0.540	13.72	71700	.75	19.1	.406	10.3	81	14	.34	8.6	27	122	.36	9.1	0.067	1.7	5.38	MW	CG	N
0.540	13.72	71700S	.75	19.1	.406	10.3	69	12	.27	6.8	19	83	.36	9.1	0.067	1.7	5.38	SST	CG	N
0.540	13.72	71636	.88	22.4	.458	11.6	11	2.0	.61	16	6.9	31	.20	5.1	0.041	1.0	4.88	MW	CG	N
0.540	13.72	71636S	.88	22.4	.458	11.6	9.5	1.7	.49	12	4.7	21	.20	5.1	0.041	1.0	4.88	SST	CG	N
0.540	13.72	71649	.88	22.4	.448	11.4	16	2.9	.59	15	9.7	43	.24	6.1	0.046	1.2	5.25	MW	CG	N
0.540	13.72	71649S	.88	22.4	.448	11.4	14	2.4	.47	12	6.5	29	.24	6.1	0.046	1.2	5.25	SST	CG	N
0.540	13.72	71662	.88	22.4	.432	11.0	29	5.1	.50	13	15	65	.30	7.7	0.054	1.4	5.63	MW	CG	N
0.540	13.72	71662S	.88	22.4	.432	11.0	25	4.4	.40	10	9.8	44	.30	7.7	0.054	1.4	5.63	SST	CG	N
0.540	13.72	71675	.88	22.4	.424	10.8	38	6.7	.47	12	18	80	.33	8.5	0.058	1.5	5.75	MW	CG	N
0.540	13.72	71675S	.88	22.4	.424	10.8	33	5.7	.37	9.5	12	54	.33	8.5	0.058	1.5	5.75	SST	CG	N
0.540	13.72	71688	.88	22.4	.414	10.5	53	9.2	.43	11	23	102	.38	9.6	0.063	1.6	6.00	MW	CG	N
0.540	13.72	71688S	.88	22.4	.414	10.5	45	7.8	.35	8.8	15	69	.38	9.6	0.063	1.6	6.00	SST	CG	N
0.540	13.72	71701	.88	22.4	.406	10.3	68	12	.41	10	27	122	.40	10.2	0.067	1.7	6.00	MW	CG	N
0.540	13.72	71701S	.88	22.4	.406	10.3	57	10	.32	8.2	19	83	.40	10.2	0.067	1.7	6.00	SST	CG	N
0.540	13.72	71637	1.00	25.4	.458	11.6	9.7	1.7	.71	18	6.9	31	.22	5.6	0.041	1.0	5.38	MW	CG	N
0.540	13.72	71637S	1.00	25.4	.458	11.6	8.2	1.4	.57	14	4.7	21	.22	5.6	0.041	1.0	5.38	SST	CG	N
0.540	13.72	71650	1.00	25.4	.448	11.4	14	2.5	.69	17	9.7	43	.26	6.7	0.046	1.2	5.75	MW	CG	N
0.540	13.72	71650S	1.00	25.4	.448	11.4	12	2.1	.55	14	6.5	29	.26	6.7	0.046	1.2	5.75	SST	CG	N
0.540	13.72	71663	1.00	25.4	.432	11.0	25	4.4	.58	15	15	65	.34	8.6	0.054	1.4	6.25	MW	CG	N
0.540	13.72	71663S	1.00	25.4	.432	11.0	21	3.8	.46	12	9.8	44	.34	8.6	0.054	1.4	6.25	SST	CG	N
0.540	13.72	71676	1.00	25.4	.424	10.8	33	5.8	.54	14	18	80	.37	9.4	0.058	1.5	6.38	MW	CG	N
0.540	13.72	71676S	1.00	25.4	.424	10.8	28	4.9	.43	11	12	54	.37	9.4	0.058	1.5	6.38	SST	CG	N
0.540	13.72	71689	1.00	25.4	.414	10.5	45	7.9	.51	13	23	102	.42	10.6	0.063	1.6	6.63	MW	CG	N
0.540	13.72	71689S	1.00	25.4	.414	10.5	38	6.7	.40	10	15	69	.42	10.6	0.063	1.6	6.63	SST	CG	N
0.540	13.72	71702	1.00	25.4	.406	10.3	58	10	.47	12	27	122	.45	11.5	0.067	1.7	6.75	MW	CG	N
0.540	13.72	71702S	1.00	25.4	.406	10.3	49	8.6	.38	9.6	19	83	.45	11.5	0.067	1.7	6.75	SST	CG	N
0.540	13.72	71638	1.25	31.8	.458	11.6	7.6	1.3	.91	23	6.9	31	.26	6.5	0.041	1.0	6.25	MW	CG	N
0.540	13.72	71638S	1.25	31.8	.458	11.6	6.5	1.1	.72	18	4.7	21	.26	6.5	0.041	1.0	6.25	SST	CG	N
0.540	13.72	71652	1.25	31.8	.448	11.4	11	1.9	.87	22	9.7	43	.32	8.0	0.046	1.2	6.88	MW	CG	N
0.540	13.72	71652S	1.25	31.8	.448	11.4	9.4	1.6	.70	18	6.5	29	.32	8.0	0.046	1.2	6.88	SST	CG	N
0.540	13.72	71664	1.25	31.8	.432	11.0	20	3.4	.74	19	15	65	.40	10.1	0.054	1.4	7.38	MW	CG	N
0.540	13.72	71664S	1.25	31.8	.432	11.0	17	2.9	.59	15	9.8	44	.40	10.1	0.054	1.4	7.38	SST	CG	N
0.540	13.72	71677	1.25	31.8	.424	10.8	26	4.5	.70	18	18	80	.44	11.2	0.058	1.5	7.63	MW	CG	N
0.540	13.72	71677S	1.25	31.8	.424	10.8	22	3.8	.56	14	12	54	.44	11.2	0.058	1.5	7.63	SST	CG	N
0.540	13.72	71690	1.25	31.8	.414	10.5	35	6.1	.65	17	23	102	.50	12.8	0.063	1.6	8.00	MW	CG	N
0.540	13.72	71690S	1.25	31.8	.414	10.5	30	5.2	.52	13	15	69	.50	12.8	0.063	1.6	8.00	SST	CG	N
0.540	13.72	71703	1.25	31.8	.406	10.3	45	7.8	.61	16	27	122	.54	13.8	0.067	1.7	8.13	MW	CG	N
0.540	13.72	71703S	1.25	31.8	.406	10.3	38	6.7	.49	12	19	83	.54	13.8	0.067	1.7	8.13	SST	CG	N
0.540	13.72	71639	1.50	38.1	.458	11.6	6.3	1.1	1.1	28	6.9	31	.30	7.6	0.041	1.0	7.25	MW	CG	N
0.540	13.72	71639S	1.50	38.1	.458	11.6	5.3	.93	.88	22	4.7	21	.30	7.6	0.041	1.0	7.25	SST	CG	N
0.540	13.72	71651	1.50	38.1	.448	11.4	9.1	1.6	1.1	27	9.7	43	.36	9.2	0.046	1.2	7.88	MW	CG	N
0.540	13.72	71651S	1.50	38.1	.448	11.4	7.7	1.4	.85	21	6.5	29	.36	9.2	0.046	1.2	7.88	SST	CG	N
0.540	13.72	71665	1.50	38.1	.432	11.0	16	2.8	.90	23	15	65	.47	11.8	0.054	1.4	8.63	MW	CG	N
0.540	13.72	71665S	1.50	38.1	.432	11.0	14	2.4	.72	18	9.8	44	.47	11.8	0.054	1.4	8.63	SST	CG	N
0.540	13.72	71678																		



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.540	13.72	71667S	2.00	50.8	.432	11.0	10	1.8	.97	25	9.8	44	.59	15.1	0.054	1.4	11.0	SST	CG	N
0.540	13.72	71680	2.00	50.8	.424	10.8	16	2.7	1.2	29	18	80	.66	16.8	0.058	1.5	11.4	MW	CG	N
0.540	13.72	71680S	2.00	50.8	.424	10.8	13	2.3	.92	23	12	54	.66	16.8	0.058	1.5	11.4	SST	CG	N
0.540	13.72	71693	2.00	50.8	.414	10.5	21	3.7	1.1	28	23	102	.75	19.0	0.063	1.6	11.9	MW	CG	N
0.540	13.72	71693S	2.00	50.8	.414	10.5	18	3.1	.87	22	15	69	.75	19.0	0.063	1.6	11.9	SST	CG	N
0.540	13.72	71706	2.00	50.8	.406	10.3	27	4.7	1.0	26	27	122	.82	20.8	0.067	1.7	12.3	MW	CG	N
0.540	13.72	71706S	2.00	50.8	.406	10.3	23	4.0	.81	21	19	83	.82	20.8	0.067	1.7	12.3	SST	CG	N
0.540	13.72	71642	2.25	57.2	.458	11.6	4.1	.72	1.7	43	6.9	31	.41	10.4	0.041	1.0	10.0	MW	CG	N
0.540	13.72	71642S	2.25	57.2	.458	11.6	3.5	.61	1.3	34	4.7	21	.41	10.4	0.041	1.0	10.0	SST	CG	N
0.540	13.72	71655	2.25	57.2	.448	11.4	5.9	1.0	1.6	41	9.7	43	.51	12.9	0.046	1.2	11.0	MW	CG	N
0.540	13.72	71655S	2.25	57.2	.448	11.4	5.0	.88	1.3	33	6.5	29	.51	12.9	0.046	1.2	11.0	SST	CG	N
0.540	13.72	71668	2.25	57.2	.432	11.0	11	1.8	1.4	35	15	65	.65	16.6	0.054	1.4	12.1	MW	CG	N
0.540	13.72	71668S	2.25	57.2	.432	11.0	8.9	1.6	1.1	28	9.8	44	.65	16.6	0.054	1.4	12.1	SST	CG	N
0.540	13.72	71681	2.25	57.2	.424	10.8	14	2.4	1.3	33	18	80	.73	18.6	0.058	1.5	12.6	MW	CG	N
0.540	13.72	71681S	2.25	57.2	.424	10.8	12	2.0	1.0	27	12	54	.73	18.6	0.058	1.5	12.6	SST	CG	N
0.540	13.72	71694	2.25	57.2	.414	10.5	19	3.3	1.2	31	23	102	.83	21.2	0.063	1.6	13.3	MW	CG	N
0.540	13.72	71694S	2.25	57.2	.414	10.5	16	2.8	.98	25	15	69	.83	21.2	0.063	1.6	13.3	SST	CG	N
0.540	13.72	71707	2.25	57.2	.406	10.3	24	4.1	1.2	29	27	122	.91	23.2	0.067	1.7	13.6	MW	CG	N
0.540	13.72	71707S	2.25	57.2	.406	10.3	20	3.5	.92	23	19	83	.91	23.2	0.067	1.7	13.6	SST	CG	N
0.540	13.72	71643	2.50	63.5	.458	11.6	3.7	.64	1.9	48	6.9	31	.45	11.3	0.041	1.0	10.9	MW	CG	N
0.540	13.72	71643S	2.50	63.5	.458	11.6	3.1	.55	1.5	38	4.7	21	.45	11.3	0.041	1.0	10.9	SST	CG	N
0.540	13.72	71656	2.50	63.5	.448	11.4	5.3	.93	1.8	46	9.7	43	.55	14.0	0.046	1.2	12.0	MW	CG	N
0.540	13.72	71656S	2.50	63.5	.448	11.4	4.5	.79	1.4	37	6.5	29	.55	14.0	0.046	1.2	12.0	SST	CG	N
0.540	13.72	71669	2.50	63.5	.432	11.0	9.4	1.6	1.5	39	15	65	.72	18.3	0.054	1.4	13.4	MW	CG	N
0.540	13.72	71669S	2.50	63.5	.432	11.0	8.0	1.4	1.2	31	9.8	44	.72	18.3	0.054	1.4	13.4	SST	CG	N
0.540	13.72	71682	2.50	63.5	.424	10.8	12	2.1	1.5	37	18	80	.80	20.4	0.058	1.5	13.9	MW	CG	N
0.540	13.72	71682S	2.50	63.5	.424	10.8	10	1.8	1.2	30	12	54	.80	20.4	0.058	1.5	13.9	SST	CG	N
0.540	13.72	71695	2.50	63.5	.414	10.5	17	2.9	1.4	35	23	102	.92	23.4	0.063	1.6	14.6	MW	CG	N
0.540	13.72	71695S	2.50	63.5	.414	10.5	14	2.5	1.1	28	15	69	.92	23.4	0.063	1.6	14.6	SST	CG	N
0.540	13.72	71708	2.50	63.5	.406	10.3	21	3.7	1.3	33	27	122	1.01	25.5	0.067	1.7	15.0	MW	CG	N
0.540	13.72	71708S	2.50	63.5	.406	10.3	18	3.1	1.0	26	19	83	1.01	25.5	0.067	1.7	15.0	SST	CG	N
0.540	13.72	71644	2.75	69.9	.458	11.6	3.3	.58	2.1	53	6.9	31	.49	12.4	0.041	1.0	11.9	MW	CG	N
0.540	13.72	71644S	2.75	69.9	.458	11.6	2.8	.49	1.6	42	4.7	21	.49	12.4	0.041	1.0	11.9	SST	CG	N
0.540	13.72	71657	2.75	69.9	.448	11.4	4.8	.84	2.0	51	9.7	43	.60	15.3	0.046	1.2	13.1	MW	CG	N
0.540	13.72	71657S	2.75	69.9	.448	11.4	4.1	.72	1.6	41	6.5	29	.60	15.3	0.046	1.2	13.1	SST	CG	N
0.540	13.72	71670	2.75	69.9	.432	11.0	8.5	1.5	1.7	43	15	65	.78	19.9	0.054	1.4	14.5	MW	CG	N
0.540	13.72	71670S	2.75	69.9	.432	11.0	7.2	1.3	1.4	35	9.8	44	.78	19.9	0.054	1.4	14.5	SST	CG	N
0.540	13.72	71683	2.75	69.9	.424	10.8	11	1.9	1.6	41	18	80	.88	22.5	0.058	1.5	15.3	MW	CG	N
0.540	13.72	71683S	2.75	69.9	.424	10.8	9.4	1.6	1.3	33	12	54	.88	22.5	0.058	1.5	15.3	SST	CG	N
0.540	13.72	71696	2.75	69.9	.414	10.5	15	2.6	1.5	39	23	102	1.00	25.4	0.063	1.6	15.9	MW	CG	N
0.540	13.72	71696S	2.75	69.9	.414	10.5	13	2.2	1.2	31	15	69	1.00	25.4	0.063	1.6	15.9	SST	CG	N
0.540	13.72	71709	2.75	69.9	.406	10.3	19	3.3	1.4	36	27	122	1.10	27.9	0.067	1.7	16.4	MW	CG	N
0.540	13.72	71709S	2.75	69.9	.406	10.3	16	2.8	1.1	29	19	83	1.10	27.9	0.067	1.7	16.4	SST	CG	N
0.540	13.72	71645	3.00	76.2	.458	11.6	3.0	.53	2.3	57	6.9	31	.52	13.3	0.041	1.0	12.8	MW	CG	N
0.540	13.72	71645S	3.00	76.2	.458	11.6	2.6	.45	1.8	46	4.7	21	.52	13.3	0.041	1.0	12.8	SST	CG	N
0.540	13.72	71658	3.00	76.2	.448	11.4	4.4	.77	2.2	56	9.7	43	.65	16.5	0.046	1.2	14.1	MW	CG	N
0.540	13.72	71658S	3.00	76.2	.448	11.4	3.7	.66	1.7	44	6.5	29	.65	16.5	0.046	1.2	14.1	SST	CG	N
0.540	13.72	71671	3.00	76.2	.432	11.0	7.8	1.4	1.9	48	15	65	.85	21.6	0.054	1.4	15.8	MW	CG	N
0.540	13.72	71671S	3.00	76.2	.432	11.0	6.6	1.2	1.5	38	9.8	44	.85	21.6	0.054	1.4	15.8	SST	CG	N
0.540	13.72	71684	3.00	76.2	.424	10.8	10	1.8	1.8	45	18	80	.95	24.1	0.058	1.5	16.4	MW	CG	N
0.540	13.72	71684S	3.00	76.2	.424	10.8	8.6	1.5	1.4	36	12	54	.95	24.1	0.058	1.5	16.4	SST	CG	N
0.540	13.72	71697	3.00	76.2	.414	10.5	14	2.4	1.7	42	23	102	1.09	27.6	0.063	1.6	17.3	MW	CG	N
0.540	13.72	71697S	3.00	76.2	.414	10.5	12	2.0	1.3	34	15	69	1.09	27.6	0.063	1.6	17.3	SST	CG	N
0.540	13.72	71710	3.00	76.2	.406	10.3	18	3.1	1.6	40	27	122	1.18	30.0	0.067	1.7	17.6	MW	CG	N
0.540	13.72	71710S	3.00	76.2	.406	10.3	15	2.6	1.2	32	19	83	1.18	30.0	0.067	1.7	17.6	SST	CG	N
0.546	13.87	S-56	.28	7.1	.484	12.3	4.3	.75	.13	3.2	.54	2.4	.16	3.9	0.031	0.8	4.00	SST	C	N
0.546	13.87	A9-48	.31	7.9	.454	11.5	23	4.0	.13	3.3	2.9	13	.18	4.7	0.046	1.2	4.00	SST		



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.546	13.87	2953	.69	17.4	.498	12.6	.79	.14	.54	14	.42	1.9	.15	3.8	0.024	0.6	6.25	MW	CG	Z
0.546	13.87	BB-69	.69	17.4	.486	12.3	1.9	.33	.49	12	.93	4.1	.20	5.0	0.030	0.8	6.50	MW	CG	BO
0.546	13.87	G-92	.69	17.4	.470	11.9	7.2	1.3	.51	13	3.7	16	.18	4.6	0.038	1.0	4.75	SST	CG	N
0.546	13.87	A9-68	.69	17.4	.452	11.5	14	2.5	.41	10	5.7	25	.28	7.2	0.047	1.2	6.00	SPR	CG	N
0.546	13.87	A13-24	.69	17.4	.434	11.0	39	6.8	.28	7.1	11	48	.27	6.8	0.056	1.4	4.75	SST	CG	N
0.546	13.87	B6-68	.72	18.2	.476	12.1	8.1	1.4	.38	9.7	3.1	14	.14	3.6	0.035	0.9	4.00	SPR	CG	N
0.546	13.87	A13-48	.72	18.2	.468	11.9	11	2.0	.35	8.9	4.0	18	.16	4.0	0.039	1.0	4.00	SST	CG	N
0.546	13.87	JJ-93	.75	19.1	.466	11.8	14	2.5	.32	8.2	4.6	20	.20	5.1	0.040	1.0	4.00	SPR	C	N
0.546	13.87	10054	.75	19.1	.456	11.6	19	3.3	.35	8.8	6.5	29	.20	5.1	0.045	1.1	4.50	SPR	CG	GI
0.546	13.87	B14-34	.75	19.1	.454	11.5	6.4	1.1	.24	6.2	1.6	7.0	.51	12.9	0.046	1.2	10.0	SPR	C	Z
0.546	13.87	S-1408	.75	19.1	.434	11.0	42	7.3	.26	6.6	11	48	.31	7.8	0.056	1.4	4.50	SST	C	N
0.546	13.87	K-61	.75	19.1	.422	10.7	36	6.3	.35	8.8	13	56	.40	10.2	0.062	1.6	6.50	SST	CG	N
0.546	13.87	3597	.75	19.1	.420	10.7	67	12	.34	8.6	23	101	.32	8.0	0.063	1.6	5.00	MW	CG	Z
0.546	13.87	VW-64	.75	19.1	.402	10.2	121	21	.19	4.8	23	102	.36	9.1	0.072	1.8	5.00	HD	CG	Z
0.546	13.87	A14-57	.78	19.8	.434	11.0	36	6.2	.31	7.8	11	48	.28	7.1	0.056	1.4	5.00	SST	CG	N
0.546	13.87	10662	.81	20.6	.504	12.8	.55	.10	.68	17	.37	1.7	.14	3.5	0.021	0.5	5.50	MW	C	Z
0.546	13.87	A11-59	.81	20.6	.464	11.8	7.9	1.4	.57	14	4.5	20	.25	6.2	0.041	1.0	6.00	SPR	CG	Z
0.546	13.87	A15-57	.81	20.6	.456	11.6	14	2.4	.44	11	6.1	27	.23	5.7	0.045	1.1	5.00	SST	CG	N
0.546	13.87	S-1194	.81	20.6	.422	10.7	65	11	.22	5.7	15	65	.28	7.1	0.062	1.6	4.50	SST	CG	N
0.546	13.87	B1-30	.81	20.6	.418	10.6	55	9.6	.29	7.5	16	71	.35	8.9	0.064	1.6	5.50	SST	CG	N
0.546	13.87	A-60	.81	20.6	.356	9.0	319	56	.15	3.9	49	218	.57	14.5	0.095	2.4	6.00	SPR	CG	Z
0.546	13.87	G-81	.84	21.4	.482	12.2	1.9	.34	.60	15	1.1	5.1	.25	6.3	0.032	0.8	7.75	HD	CG	N
0.546	13.87	S-1633	.84	21.4	.464	11.8	10	1.8	.45	11	4.6	20	.19	4.9	0.041	1.0	4.75	SST	CG	N
0.546	13.87	S-1049	.88	22.2	.422	10.7	47	8.2	.31	8.0	15	65	.34	8.7	0.062	1.6	5.50	SST	CG	N
0.546	13.87	G-50	.88	22.2	.402	10.2	90	16	.24	6.0	21	95	.40	10.1	0.072	1.8	5.50	SST	CG	N
0.546	13.87	L-26	.88	22.2	.402	10.2	84	15	.25	6.5	21	95	.41	10.5	0.072	1.8	5.75	SST	CG	N
0.546	13.87	A13-61	.91	23.0	.416	10.6	61	11	.29	7.4	18	79	.37	9.5	0.065	1.7	5.75	SPR	CG	GI
0.546	13.87	S-869	.94	23.8	.484	12.3	2.1	.37	.75	19	1.6	7.1	.19	4.7	0.031	0.8	6.00	SST	CG	N
0.546	13.87	10176	.94	23.8	.452	11.5	7.5	1.3	.44	11	3.3	15	.49	12.5	0.047	1.2	9.50	SPR	C	Z
0.546	13.87	S-1061	1.00	25.4	.472	12.0	5.9	1.0	.57	15	3.4	15	.22	5.6	0.037	0.9	5.00	SST	C	N
0.546	13.87	A15-27	1.00	25.4	.456	11.6	12	2.1	.51	13	6.1	27	.25	6.3	0.045	1.1	5.50	SST	CG	N
0.546	13.87	S-271	1.00	25.4	.438	11.1	18	3.1	.55	14	9.7	43	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.546	13.87	B1-55	1.00	25.4	.434	11.0	29	5.1	.40	10	12	51	.34	8.7	0.056	1.4	6.00	SPR	CG	GI
0.546	13.87	YY-70	1.00	25.4	.412	10.5	59	10	.33	8.5	20	87	.44	11.1	0.067	1.7	6.50	SPR	CG	Z
0.546	13.87	12327	1.09	27.8	.426	10.8	32	5.7	.44	11	14	63	.42	10.7	0.060	1.5	7.00	SPR	CG	GI
0.546	13.87	B9-32	1.13	28.6	.468	11.9	.57	.99	.75	19	4.2	19	.25	6.4	0.039	1.0	6.50	SPR	CG	Z
0.546	13.87	VV-65	1.13	28.6	.422	10.7	37	6.6	.41	11	16	69	.43	11.0	0.062	1.6	7.00	SPR	CG	N
0.546	13.87	AA-86	1.13	28.6	.366	9.3	126	22	.31	7.8	39	173	.81	20.6	0.090	2.3	9.00	SST	CG	N
0.546	13.87	10630	1.16	29.4	.488	12.4	1.3	.23	.92	23	1.2	5.4	.23	5.9	0.029	0.7	7.00	SST	C	N
0.546	13.87	H-36	1.19	30.2	.484	12.3	.62	.11	.64	16	.39	1.8	.55	14.0	0.031	0.8	17.8	MW	CG	N
0.546	13.87	A15-68	1.19	30.2	.470	11.9	4.8	.84	.77	20	3.7	16	.24	6.0	0.038	1.0	6.25	SST	CG	N
0.546	13.87	A9-57	1.19	30.2	.470	11.9	4.1	.71	.91	23	3.7	16	.27	6.8	0.038	1.0	7.00	SST	CG	N
0.546	13.87	K-55	1.19	30.2	.452	11.5	7.0	1.2	.72	18	5.0	22	.47	11.9	0.047	1.2	9.00	SST	C	N
0.546	13.87	11706	1.19	30.2	.434	11.0	20	3.5	.58	15	12	51	.45	11.4	0.056	1.4	8.00	SPR	CG	Z
0.546	13.87	W-56	1.19	30.2	.422	10.7	28	5.0	.52	13	15	65	.48	12.2	0.062	1.6	7.75	SST	CG	N
0.546	13.87	10465	1.22	31.0	.476	12.1	2.0	.34	.86	22	1.7	7.5	.36	9.1	0.035	0.9	10.3	SPR	CG	Z
0.546	13.87	I-94	1.25	31.8	.490	12.4	.52	.09	.87	22	.45	2.0	.39	9.8	0.028	0.7	12.8	SST	C	N
0.546	13.87	YY-49	1.25	31.8	.456	11.6	12	2.1	.55	14	6.5	29	.27	6.9	0.045	1.1	6.00	SPR	CG	N
0.546	13.87	RR-50	1.25	31.8	.454	11.5	11	2.0	.58	15	6.5	29	.32	8.2	0.046	1.2	6.00	SST	C	N
0.546	13.87	S-932	1.25	31.8	.452	11.5	6.9	1.2	.77	20	5.3	24	.48	12.1	0.047	1.2	9.00	SST	C	N
0.546	13.87	S-1137	1.25	31.8	.452	11.5	11	1.9	.63	16	6.9	31	.35	9.0	0.047	1.2	6.50	SST	C	N
0.546	13.87	S-2	1.25	31.8	.438	11.1	15	2.6	.66	17	9.7	43	.43	11.0	0.054	1.4	8.00	SST	CG	N
0.546	13.87	00-99	1.25	31.8	.362	9.2	96	17	.15	3.7	14	62	1.10	28.0	0.092	2.3	12.0	SST	CG	N
0.546	13.87	S-3208	1.31	33.3	.458	11.6	8.0	1.4	.71	18	5.7	25	.34	8.7	0.044	1.1	6.75	SST	C	N
0.546	13.87	S-1593	1.34	34.1	.436	11.1	14	2.5	.73	19	10	46	.55	14.0	0.055	1.4	9.00	SST	C	N
0.546	13.87	1897	1.38	34.9	.498	12.6	.52	.09	1.1	29	.59	2.6	.23	5.8	0.024	0.6	8.50	MW	C	Z
0.546	13.87	FF-92	1.38	34.9	.472	12.0	2.0	.36	.93	24	1.9	8.5	.44	11.3	0.037	0.9	12.0	SPR	CG	N
0.546	13.87	XX-48	1.38	34.9	.472	12.0	3.9	.69	.86											



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.546	13.87	10587	1.69	42.8	.456	11.6	4.6	.81	1.2	30	5.5	24	.50	12.6	0.045	1.1	11.0	SST	CG	N
0.546	13.87	12238	1.69	42.8	.446	11.3	9.2	1.6	.90	23	8.3	37	.50	12.7	0.050	1.3	10.0	SPR	CG	Z
0.546	13.87	S-972	1.69	42.8	.388	9.9	43	7.6	.65	16	28	125	1.03	26.1	0.079	2.0	13.0	SST	CG	N
0.546	13.87	G-46	1.75	44.5	.464	11.8	1.6	.28	.93	24	1.5	6.7	.82	20.8	0.041	1.0	19.0	SST	C	N
0.546	13.87	S-78	1.75	44.5	.412	10.5	25	4.3	.74	19	18	82	.82	20.8	0.067	1.7	11.3	SST	C	N
0.546	13.87	12280	1.78	45.2	.494	12.5	.36	.06	1.4	35	.49	2.2	.42	10.6	0.026	0.7	15.0	MW	C	Z
0.546	13.87	11474	1.78	45.2	.446	11.3	9.2	1.6	.90	23	8.3	37	.55	14.0	0.050	1.3	10.0	SPR	C	Z
0.546	13.87	N-118	1.81	46.0	.376	9.6	81	14	.46	12	37	165	.98	24.8	0.085	2.2	11.5	SPR	CG	Z
0.546	13.87	12217	1.84	46.8	.472	12.0	2.6	.45	1.4	36	3.6	16	.41	10.3	0.037	0.9	10.0	SPR	C	Z
0.546	13.87	3817	1.88	47.6	.362	9.2	110	19	.41	10	45	199	1.10	28.0	0.092	2.3	12.0	HD	CG	Z
0.546	13.87	S-325	1.94	49.2	.452	11.5	3.9	.67	1.2	31	4.7	21	.71	17.9	0.047	1.2	15.0	SST	CG	N
0.546	13.87	Q-44	2.00	50.8	.466	11.8	1.7	.29	1.2	31	2.1	9.2	.76	19.3	0.040	1.0	19.0	SPR	CG	N
0.546	13.87	11650	2.00	50.8	.352	8.9	108	19	.48	12	52	231	1.46	37.0	0.097	2.5	15.0	SPR	CG	Z
0.546	13.87	12309	2.09	53.2	.354	9.0	103	18	.49	12	50	224	1.44	36.6	0.096	2.4	15.0	SPR	CG	Z
0.546	13.87	S-200	2.13	54.0	.402	10.2	40	7.0	.53	14	21	95	.79	20.1	0.072	1.8	10.0	SST	C	N
0.546	13.87	J-35	2.22	56.4	.364	9.2	73	13	.59	15	43	192	1.48	37.6	0.091	2.3	16.3	SPR	CG	N
0.546	13.87	WW-37	2.50	63.5	.470	11.9	4.6	.80	.86	22	3.9	17	.30	7.7	0.038	1.0	7.00	SPR	C	N
0.546	13.87	12049	2.56	65.1	.452	11.5	5.4	.94	1.4	35	7.4	33	.59	14.9	0.047	1.2	12.5	SPR	CG	N
0.546	13.87	UU-57	2.63	66.7	.446	11.3	5.9	1.0	1.4	36	8.3	37	.73	18.4	0.050	1.3	14.5	SPR	CG	Z
0.546	13.87	11593	2.81	71.4	.386	9.8	36	6.4	.85	22	31	138	1.52	38.6	0.080	2.0	18.0	SPR	CG	GI
0.546	13.87	2595	2.94	74.6	.434	11.0	8.0	1.4	1.4	37	12	51	.95	24.2	0.056	1.4	17.0	SPR	CG	GI
0.546	13.87	12291	3.19	81.0	.446	11.3	4.1	.72	2.0	51	8.3	37	1.05	26.7	0.050	1.3	20.0	SPR	C	N
0.546	13.87	B17-197	4.06	103.2	.412	10.5	14	2.5	1.4	34	20	87	1.36	34.5	0.067	1.7	20.3	SPR	CG	Z
0.546	13.87	A14-70	4.50	114.3	.420	10.7	8.6	1.5	1.8	45	15	68	1.43	36.4	0.063	1.6	22.8	SST	CG	N
0.546	13.87	11626	5.25	133.4	.456	11.6	1.7	.30	3.7	95	6.5	29	1.31	33.1	0.045	1.1	29.0	SPR	CG	Z
0.546	13.87	4003	19.0	482.6	.422	10.7	1.8	.31	8.8	222	16	69	6.73	170.9	0.062	1.6	107.0	HD	C	Z
0.551	14.00	B3-62	3.44	87.3	.301	7.6	245	43	.42	11	102	453	2.56	65.1	0.125	3.2	20.5	SPR	CG	N
0.562	14.27	S-209	.31	7.9	.472	12.0	25	4.4	.11	2.8	2.8	12	.20	5.1	0.045	1.1	3.50	SST	C	N
0.562	14.27	A9-35	.31	7.9	.460	11.7	58	10	.15	3.7	8.5	38	.17	4.2	0.051	1.3	3.25	SPR	CG	Z
0.562	14.27	S-221	.31	7.9	.452	11.5	72	13	.13	3.4	9.5	42	.18	4.5	0.055	1.4	3.25	SST	CG	N
0.562	14.27	2956	.34	8.7	.512	13.0	1.0	.18	.18	4.6	.19	83	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.562	14.27	JJ-38	.41	10.3	.468	11.9	36	6.4	.18	4.7	6.7	30	.20	5.1	0.047	1.2	3.25	SST	C	N
0.562	14.27	II-20	.41	10.3	.402	10.2	263	46	.09	2.2	23	101	.32	8.1	0.080	2.0	4.00	SPR	CG	N
0.562	14.27	3253	.47	11.9	.452	11.5	58	10	.18	4.7	11	47	.21	5.2	0.055	1.4	3.75	SPR	CG	Z
0.562	14.27	S-1459	.50	12.7	.518	13.2	.68	.12	.37	9.5	.25	1.1	.13	3.2	0.022	0.6	4.75	SST	C	N
0.562	14.27	JJ-8	.50	12.7	.502	12.8	3.0	.53	.34	8.7	1.0	4.6	.16	4.0	0.030	0.8	4.25	SST	C	N
0.562	14.27	K-19	.50	12.7	.478	12.1	16	2.8	.29	7.4	4.6	21	.21	5.3	0.042	1.1	4.00	SPR	C	GI
0.562	14.27	DD-89	.50	12.7	.438	11.1	99	17	.14	3.7	14	63	.22	5.5	0.062	1.6	3.50	SST	CG	N
0.562	14.27	A15-43	.53	13.5	.458	11.6	23	4.1	.27	6.9	6.3	28	.26	6.6	0.052	1.3	5.00	SST	CG	N
0.562	14.27	S-1529	.53	13.5	.446	11.3	40	7.0	.26	6.5	10	46	.28	7.0	0.058	1.5	4.75	SST	CG	N
0.562	14.27	U-61	.53	13.5	.442	11.2	75	13	.17	4.4	13	58	.23	5.7	0.060	1.5	3.75	SST	CG	N
0.562	14.27	S-436	.53	13.5	.434	11.0	113	20	.14	3.5	16	70	.22	5.7	0.064	1.6	3.50	SST	CG	N
0.562	14.27	B1-32	.59	15.1	.448	11.4	59	10	.20	5.1	12	53	.23	5.8	0.057	1.4	4.00	SPR	CG	N
0.562	14.27	S-1350	.63	15.9	.530	13.5	.17	.03	.53	13	.09	.39	.10	2.4	0.016	0.4	5.00	SST	C	N
0.562	14.27	Q-48	.63	15.9	.512	13.0	1.6	.28	.50	13	.79	3.5	.13	3.2	0.025	0.6	4.00	SST	C	N
0.562	14.27	B15-33	.63	15.9	.502	12.8	2.7	.48	.46	12	1.3	5.6	.17	4.2	0.030	0.8	4.50	SST	C	N
0.562	14.27	12685	.63	15.9	.500	12.7	3.9	.68	.47	12	1.8	8.1	.16	3.9	0.031	0.8	4.00	SST	C	N
0.562	14.27	3990	.63	15.9	.446	11.3	39	6.8	.32	8.1	12	55	.30	7.7	0.058	1.5	5.25	SPR	CG	Z
0.562	14.27	S-219	.63	15.9	.438	11.1	74	13	.19	4.9	14	63	.25	6.3	0.062	1.6	4.00	SST	CG	N
0.562	14.27	12750	.63	15.9	.438	11.1	74	13	.19	4.9	14	63	.31	7.9	0.062	1.6	4.00	SST	C	N
0.562	14.27	S-33	.66	16.7	.468	11.9	18	3.2	.37	9.4	6.7	30	.21	5.4	0.047	1.2	4.50	SST	CG	N
0.562	14.27	U-32	.66	16.7	.460	11.7	22	3.8	.37	9.4	8.0	36	.26	6.5	0.051	1.3	5.00	SST	CG	N
0.562	14.27	B-6	.66	16.7	.418	10.6	119	21	.19	4.7	22	99	.34	8.7	0.072	1.8	4.75	SPR	CG	N
0.562	14.27	S-921	.66	16.7	.376	9.6	308	54	.14	3.4	42	185	.47	11.8	0.093	2.4	5.00	SST	CG	N
0.562	14.27	S-1548	.69	17.4	.434	11.0	62	11	.25	6.4	16	70	.30	7.7	0.064	1.6	4.75	SST	CG	N
0.562	14.27	3197	.72	18.2	.498	12.6	2.2	.39	.51	13	1.1	5.1	.21	5.3	0.032	0.8	6.50	SPR	CG	Z
0.562	14.27	4189	.72	18.2	.438	11.1	49	8.5	.31	7.9	15	67	.34	8.7	0.062	1.6	5.50	HD	CG	Z
0.562	14.27	BB-68	.75	19.1	.520	13.2	.51	.09	.62	16	.32	1.4	.13	3.2	0.021	0.5	5.00	SST	C	N
0.562	14.27	S-1138	.75																	



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.562	14.27	10217	.94	23.8	.428	10.9	60	10	.32	8.1	19	85	.40	10.2	0.067	1.7	6.00	SPR	CG	Z
0.562	14.27	3222	.97	24.6	.510	13.0	1.2	.21	.80	20	.97	4.3	.17	4.3	0.026	0.7	5.50	MW	C	Z
0.562	14.27	12660	.98	25.0	.510	13.0	1.1	.20	.81	21	.92	4.1	.18	4.5	0.026	0.7	5.75	MW	C	GI
0.562	14.27	L-19	1.00	25.4	.502	12.8	1.9	.34	.79	20	1.5	6.8	.21	5.3	0.030	0.8	6.00	MW	C	Z
0.562	14.27	10343	1.00	25.4	.494	12.5	2.6	.46	.73	18	1.9	8.5	.27	6.9	0.034	0.9	7.00	SPR	C	Z
0.562	14.27	S-1141	1.00	25.4	.494	12.5	3.0	.53	.77	20	2.3	10	.23	5.8	0.034	0.9	5.75	SST	C	N
0.562	14.27	S-1028	1.00	25.4	.492	12.5	3.2	.56	.79	20	2.5	11	.21	5.3	0.035	0.9	6.00	SST	CG	N
0.562	14.27	S-1305	1.00	25.4	.488	12.4	5.4	.95	.61	16	3.3	15	.19	4.7	0.037	0.9	5.00	SST	CG	N
0.562	14.27	Y-27	1.00	25.4	.482	12.2	7.4	1.3	.60	15	4.4	20	.22	5.6	0.040	1.0	5.50	SPR	CG	Z
0.562	14.27	S-1027	1.00	25.4	.468	11.9	11	1.9	.63	16	6.7	30	.29	7.5	0.047	1.2	6.25	SST	CG	N
0.562	14.27	3881	1.00	25.4	.466	11.8	14	2.5	.54	14	7.6	34	.29	7.3	0.048	1.2	6.00	SPR	CG	GI
0.562	14.27	S-358	1.00	25.4	.464	11.8	15	2.7	.50	13	7.6	34	.27	6.8	0.049	1.2	5.50	SST	CG	N
0.562	14.27	12294	1.00	25.4	.458	11.6	20	3.5	.46	12	9.0	40	.31	7.9	0.052	1.3	6.00	SPR	CG	Z
0.562	14.27	11747	1.00	25.4	.456	11.6	14	2.5	.58	15	8.3	37	.42	10.8	0.053	1.3	8.00	SPR	CG	Z
0.562	14.27	515	1.00	25.4	.454	11.5	22	3.8	.47	12	10	45	.40	10.1	0.054	1.4	6.33	HD	C	Z
0.562	14.27	S-3128	1.00	25.4	.454	11.5	16	2.8	.58	15	9.5	42	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.562	14.27	3578	1.00	25.4	.452	11.5	22	3.9	.64	16	14	64	.36	9.1	0.055	1.4	6.50	MW	CG	Z
0.562	14.27	A14-33	1.00	25.4	.452	11.5	21	3.6	.48	12	10	45	.35	8.8	0.055	1.4	6.33	SST	CG	N
0.562	14.27	11544	1.00	25.4	.426	10.8	57	9.9	.35	8.9	20	88	.51	13.0	0.068	1.7	6.50	SPR	CG	N
0.562	14.27	S-1242	1.00	25.4	.418	10.6	71	13	.29	7.4	21	93	.43	11.0	0.072	1.8	6.00	SST	CG	N
0.562	14.27	2750	1.00	25.4	.402	10.2	78	14	.38	9.6	29	131	.62	15.8	0.080	2.0	8.00	HD	CG	Z
0.562	14.27	10950	1.00	25.4	.400	10.2	110	19	.27	6.8	29	131	.53	13.4	0.081	2.1	6.50	SST	CG	N
0.562	14.27	S-801	1.03	26.2	.438	11.1	26	4.6	.54	14	14	63	.48	12.2	0.062	1.6	7.75	SST	CG	N
0.562	14.27	A11-50	1.06	27.0	.492	12.5	2.9	.52	.78	20	2.3	10	.28	7.1	0.035	0.9	7.00	SPR	C	Z
0.562	14.27	830	1.06	27.0	.352	8.9	318	56	.20	5.1	64	283	.81	20.7	0.105	2.7	7.75	HD	CG	Z
0.562	14.27	B14-68	1.13	28.6	.518	13.2	.43	.07	.95	24	.41	1.8	.18	4.5	0.022	0.6	7.00	MW	C	Z
0.562	14.27	O-89	1.13	28.6	.516	13.1	.51	.09	.94	24	.48	2.2	.18	4.7	0.023	0.6	7.00	MW	C	N
0.562	14.27	10047	1.13	28.6	.512	13.0	.73	.13	.93	23	.68	3.0	.20	5.1	0.025	0.6	7.00	MW	C	Z
0.562	14.27	B9-34	1.13	28.6	.478	12.1	4.5	.80	.75	19	3.4	15	.38	9.6	0.042	1.1	9.00	SPR	CG	Z
0.562	14.27	12561	1.13	28.6	.462	11.7	11	2.0	.68	17	7.5	33	.45	11.4	0.050	1.3	8.00	SPR	C	N
0.562	14.27	VW-40	1.13	28.6	.410	10.4	70	12	.37	9.5	26	116	.61	15.4	0.076	1.9	8.00	SPR	CG	Z
0.562	14.27	3871	1.13	28.6	.402	10.2	88	15	.35	8.8	30	135	.64	16.3	0.080	2.0	8.00	HD	CG	Z
0.562	14.27	DD-87	1.13	28.6	.402	10.2	131	23	.23	5.8	30	135	.48	12.2	0.080	2.0	6.00	SPR	CG	N
0.562	14.27	S-1534	1.22	31.0	.388	9.9	134	23	.27	6.9	36	161	.61	15.5	0.087	2.2	7.00	SST	CG	N
0.562	14.27	S-1369	1.25	31.8	.522	13.3	.31	.05	1.1	28	.35	1.6	.14	3.6	0.020	0.5	6.00	SST	C	N
0.562	14.27	3563	1.25	31.8	.512	13.0	.40	.07	.95	24	.38	1.7	.30	7.7	0.025	0.6	11.0	MW	C	GI
0.562	14.27	S-925	1.25	31.8	.478	12.1	4.9	.86	.88	22	4.3	19	.37	9.3	0.042	1.1	7.75	SST	C	N
0.562	14.27	S-1303	1.25	31.8	.474	12.0	7.9	1.4	.70	18	5.5	25	.28	7.0	0.044	1.1	6.25	SST	CG	N
0.562	14.27	3822	1.25	31.8	.466	11.8	10	1.8	.75	19	7.6	34	.36	9.1	0.048	1.2	7.50	SPR	CG	Z
0.562	14.27	10103	1.25	31.8	.460	11.7	12	2.1	.70	18	8.5	38	.41	10.4	0.051	1.3	8.00	SPR	CG	Z
0.562	14.27	3019	1.31	33.3	.402	10.2	70	12	.43	11	30	135	.76	19.3	0.080	2.0	9.50	SPR	CG	Z
0.562	14.27	12403	1.34	34.1	.512	13.0	.56	.10	1.1	28	.62	2.7	.24	6.0	0.025	0.6	8.50	MW	C	N
0.562	14.27	12026	1.34	34.1	.398	10.1	78	14	.41	11	33	145	.78	19.8	0.082	2.1	9.50	SPR	CG	N
0.562	14.27	Y-19	1.34	34.1	.352	8.9	262	46	.24	6.2	64	283	.95	24.0	0.105	2.7	9.00	SPR	CG	Z
0.562	14.27	1943	1.38	34.9	.512	13.0	.56	.10	1.1	29	.63	2.8	.24	6.0	0.025	0.6	8.50	MW	C	Z
0.562	14.27	10246	1.38	34.9	.510	13.0	.34	.06	.97	25	.32	1.4	.41	10.4	0.026	0.7	14.8	MW	C	Z
0.562	14.27	S-861	1.38	34.9	.460	11.7	7.9	1.4	.87	22	6.9	30	.51	13.0	0.051	1.3	10.0	SST	CG	N
0.562	14.27	3886	1.38	34.9	.452	11.5	13	2.2	.77	20	9.7	43	.61	15.4	0.055	1.4	10.0	SPR	C	Z
0.562	14.27	S-421	1.38	34.9	.436	11.1	25	4.4	.59	15	15	66	.52	13.2	0.063	1.6	8.25	SST	CG	N
0.562	14.27	29	1.38	34.9	.418	10.6	45	7.9	.49	12	22	99	.74	18.7	0.072	1.8	9.25	HD	C	Z
0.562	14.27	Q-29	1.38	34.9	.378	9.6	108	19	.37	9.5	40	180	.92	23.4	0.092	2.3	10.0	SST	CG	N
0.562	14.27	S-1691	1.41	35.7	.526	13.4	.03	.01	.87	22	.03	.12	.54	13.6	0.018	0.5	28.8	SST	C	N
0.562	14.27	Y-22	1.41	35.7	.512	13.0	.63	.11	1.2	31	.76	3.4	.20	5.1	0.025	0.6	7.00	MW	C	N
0.562	14.27	S-819	1.41	35.7	.418	10.6	38	6.6	.56	14	21	93	.70	17.8	0.072	1.8	9.75	SST	CG	N
0.562	14.27	3204	1.44	36.5	.504	12.8	.53	.09	.98	25	.52	2.3	.46	11.6	0.029	0.7	14.8	MW	C	Z
0.562	14.27	A9-29	1.44	36.5	.400	10.2	68	12	.43	11	29	131	.75	19.0	0.081	2.1	9.25	SST	CG	N
0.562	14.27	G-44	1.50	38.1	.506	12.9	.45	.08	1.1	27	.47	2.1	.45	11.4	0.028	0.7	15.0	MW	C	N
0.562	14.27	11365	1.50	38.1																



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./in.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.562	14.27	S-1172	1.88	47.6	.462	11.7	7.3	1.3	1.0	26	7.6	34	.50	12.7	0.050	1.3	10.0	SST	CG	N
0.562	14.27	10927	1.88	47.6	.432	11.0	21	3.8	.81	21	17	77	.83	21.1	0.065	1.7	11.8	SPR	C	Z
0.562	14.27	B2-55	1.88	47.6	.422	10.7	48	8.5	.42	11	21	91	.56	14.2	0.070	1.8	8.00	SPR	CG	N
0.562	14.27	B14-19	1.88	47.6	.384	9.8	85	15	.48	12	41	183	1.16	29.4	0.089	2.3	12.0	SPR	C	Z
0.562	14.27	12607	2.00	50.8	.490	12.4	2.1	.36	1.6	41	3.3	15	.40	10.1	0.036	0.9	10.0	MW	C	Z
0.562	14.27	11748	2.00	50.8	.460	11.7	6.1	1.1	1.3	33	7.8	35	.71	18.1	0.051	1.3	14.0	SPR	CG	Z
0.562	14.27	11440	2.00	50.8	.438	11.1	15	2.6	.94	24	14	63	.74	18.9	0.062	1.6	12.0	SST	CG	N
0.562	14.27	10066	2.00	50.8	.412	10.5	39	6.9	.64	16	25	112	.90	22.9	0.075	1.9	12.0	SPR	CG	Z
0.562	14.27	B11-46	2.00	50.8	.412	10.5	33	5.8	.71	18	23	105	.94	23.8	0.075	1.9	12.5	SST	CG	N
0.562	14.27	2898	2.06	52.4	.502	12.8	.61	.11	1.6	40	.96	4.3	.47	12.0	0.030	0.8	14.8	MW	C	Z
0.562	14.27	11874	2.09	53.2	.452	11.5	7.2	1.3	1.2	31	8.8	39	.88	22.4	0.055	1.4	16.0	SPR	CG	N
0.562	14.27	B8-48	2.16	54.8	.362	9.2	112	20	.49	13	55	246	1.50	38.1	0.100	2.5	15.0	SPR	CG	N
0.562	14.27	11568	2.22	56.4	.458	11.6	7.2	1.3	1.3	32	9.0	40	.73	18.5	0.052	1.3	13.0	SPR	CG	N
0.562	14.27	3556	2.25	57.2	.426	10.8	20	3.5	1.2	32	25	111	1.00	25.5	0.068	1.7	14.8	MW	CG	Z
0.562	14.27	10337	2.31	58.7	.428	10.9	22	3.8	.88	22	19	85	.87	22.1	0.067	1.7	13.0	SPR	CG	Z
0.562	14.27	4368	2.31	58.7	.394	10.0	56	9.8	.63	16	35	155	1.16	29.3	0.084	2.1	13.8	SPR	CG	Z
0.562	14.27	S-1219	2.38	60.3	.482	12.2	1.3	.23	1.6	40	2.1	9.3	.80	20.3	0.040	1.0	19.0	SST	C	N
0.562	14.27	3969	2.38	60.3	.472	12.0	5.3	.93	1.2	30	6.3	28	.50	12.6	0.045	1.1	10.0	SPR	C	Z
0.562	14.27	887	2.38	60.3	.402	10.2	38	6.6	.81	20	30	135	1.36	34.5	0.080	2.0	16.0	HD	C	Z
0.562	14.27	10563	2.44	61.9	.388	9.9	50	8.7	.78	20	39	172	1.52	38.7	0.087	2.2	17.5	SPR	CG	Z
0.562	14.27	4372	2.44	61.9	.336	8.5	192	34	.39	10	76	337	1.75	44.5	0.113	2.9	15.5	SPR	CG	Z
0.562	14.27	11209	2.63	66.7	.502	12.8	.61	.11	2.2	55	1.3	5.8	.47	12.0	0.030	0.8	14.8	MW	C	Z
0.562	14.27	12597	2.70	68.6	.338	8.6	177	31	.42	11	74	328	1.90	48.4	0.112	2.8	16.0	HD	C	N
0.562	14.27	10308	2.75	69.9	.418	10.6	23	4.1	.95	24	22	99	1.15	29.3	0.072	1.8	16.0	SPR	CG	Z
0.562	14.27	11279	2.75	69.9	.366	9.3	74	13	.71	18	52	232	1.96	49.8	0.098	2.5	20.0	SPR	CG	Z
0.562	14.27	2987	2.94	74.6	.278	7.1	563	99	.24	6.2	138	614	2.27	57.7	0.142	3.6	16.0	SPR	CG	Z
0.562	14.27	20	3.00	76.2	.454	11.5	6.3	1.1	1.6	40	10	45	.96	24.4	0.054	1.4	16.8	HD	C	Z
0.562	14.27	11580	3.09	78.6	.448	11.4	9.1	1.6	1.3	33	12	53	.91	23.2	0.057	1.4	15.0	SPR	CG	N
0.562	14.27	S-1107	3.13	79.4	.434	11.0	9.4	1.7	1.7	42	16	70	1.28	32.5	0.064	1.6	20.0	SST	CG	N
0.562	14.27	3695	3.16	80.2	.462	11.7	3.7	.65	2.1	53	7.8	35	1.05	26.7	0.050	1.3	20.0	SPR	C	Z
0.562	14.27	12601	3.50	88.9	.384	9.8	41	7.1	1.4	35	55	246	2.14	54.3	0.089	2.3	23.0	MW	C	N
0.562	14.27	1813	3.50	88.9	.302	7.7	272	48	.40	10	109	483	2.70	68.5	0.130	3.3	20.8	SPR	CG	Z
0.562	14.27	2737	3.75	95.3	.418	10.6	14	2.4	1.6	41	22	99	1.87	47.5	0.072	1.8	26.0	SPR	CG	Z
0.562	14.27	1887	3.75	95.3	.352	8.9	109	19	.81	21	89	395	1.97	50.0	0.105	2.7	18.8	MW	CG	Z
0.562	14.27	3438	4.00	101.6	.368	9.3	58	10	.88	22	51	225	2.33	59.1	0.097	2.5	24.0	SPR	CG	Z
0.562	14.27	S-1176	4.44	112.7	.374	9.5	48	8.3	.90	23	43	191	2.07	52.5	0.094	2.4	22.0	SST	CG	N
0.562	14.27	11287	4.50	114.3	.448	11.4	4.8	.84	2.5	62	12	53	1.57	39.8	0.057	1.4	26.5	SPR	C	Z
0.562	14.27	10342	4.88	123.8	.402	10.2	18	3.1	1.7	44	30	135	2.64	67.1	0.080	2.0	32.0	SPR	C	Z
0.562	14.27	10234	5.25	133.4	.322	8.2	113	20	.79	20	90	398	3.90	99.1	0.120	3.0	32.5	SPR	CG	Z
0.562	14.27	10786	5.50	139.7	.422	10.7	7.8	1.4	2.6	67	21	91	2.73	69.3	0.070	1.8	39.0	SPR	CG	N
0.562	14.27	10385	10.0	254.0	.438	11.1	3.9	.68	3.9	100	15	67	2.91	74.0	0.062	1.6	46.0	SPR	C	Z
0.562	14.27	10296	10.0	254.0	.432	11.0	4.8	.83	3.7	93	17	77	2.99	75.9	0.065	1.7	46.0	SPR	CG	Z
0.562	14.27	4166	12.8	323.9	.460	11.7	1.3	.24	6.3	160	8.5	38	2.91	73.8	0.051	1.3	56.0	SPR	C	Z
0.562	14.27	4392	15.0	381.0	.460	11.7	1.3	.24	6.3	160	8.5	38	2.91	73.8	0.051	1.3	56.0	SPR	C	Z
0.578	14.68	L-20	.47	11.9	.494	12.5	25	4.4	.19	4.7	4.7	21	.17	4.3	0.042	1.1	3.00	SST	C	N
0.578	14.68	WW-69	.50	12.7	.516	13.1	2.0	.36	.28	7.2	.57	2.6	.22	5.5	0.031	0.8	6.00	MW	C	Z
0.578	14.68	S-1103	.50	12.7	.502	12.8	9.5	1.7	.32	8.1	3.0	13	.18	4.6	0.038	1.0	3.75	SST	C	N
0.578	14.68	BB-80	.59	15.1	.418	10.6	138	24	.19	4.9	27	119	.40	10.2	0.080	2.0	5.00	SST	CG	N
0.578	14.68	Z-99	.63	15.9	.538	13.7	.15	.03	.41	10	.06	.26	.22	5.6	0.020	0.5	11.0	MW	CG	Z
0.578	14.68	10394	.66	16.7	.410	10.4	237	42	.14	3.6	34	151	.38	9.6	0.084	2.1	4.50	SPR	CG	Z
0.578	14.68	I-41	.69	17.4	.388	9.9	320	56	.15	3.7	47	207	.50	12.7	0.095	2.4	5.25	SPR	CG	N
0.578	14.68	G-32	.75	19.1	.524	13.3	.65	.11	.48	12	.31	1.4	.27	6.9	0.027	0.7	9.00	MW	C	Z
0.578	14.68	2718	.75	19.1	.518	13.2	2.4	.41	.57	14	1.3	6.0	.18	4.6	0.030	0.8	5.00	MW	C	Z
0.578	14.68	B14-2	.75	19.1	.484	12.3	16	2.7	.45	11	7.0	31	.24	6.0	0.047	1.2	5.00	SPR	CG	N
0.578	14.68	3659	.75	19.1	.474	12.0	29	5.1	.30	7.7	8.8	39	.23	5.9	0.052	1.3	4.50	SPR	CG	GI
0.578	14.68	J-15	.81	20.6	.454	11.5	52	9.0	.29	7.3	15	66	.31	7.9	0.062	1.6	5.00	SPR	CG	Z
0.578	14.68	A-45	.81	20.6	.418	10.6	104	18	.27	6.8	28	123	.48	12.2	0.080	2.0	6.00	SST	CG	N
0.578	14.68	12200	.88</																	



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.578	14.68	S-1498	1.31	33.3	.478	12.1	7.6	1.3	.86	22	6.5	29	.45	11.4	0.050	1.3	9.00	SST	CG	N
0.578	14.68	3112	1.31	33.3	.468	11.9	18	3.2	.56	14	10	46	.39	9.8	0.055	1.4	7.00	SPR	CG	Z
0.578	14.68	S-139	1.34	34.1	.526	13.4	.97	.17	1.2	30	1.1	5.1	.17	4.3	0.026	0.7	5.50	SST	C	N
0.578	14.68	GG-89	1.38	34.9	.450	11.4	29	5.0	.53	14	15	68	.48	12.2	0.064	1.6	7.50	SST	CG	N
0.578	14.68	WW-30	1.38	34.9	.328	8.3	539	94	.18	4.6	98	437	1.13	28.6	0.125	3.2	9.00	SPR	CG	Z
0.578	14.68	A-97	1.41	35.7	.338	8.6	443	78	.20	5.0	88	390	1.08	27.4	0.120	3.0	9.00	HD	CG	Z
0.578	14.68	10672	1.44	36.5	.438	11.1	34	5.9	.59	15	20	89	.68	17.3	0.070	1.8	9.75	SPR	CG	Z
0.578	14.68	B12-59	1.44	36.5	.396	10.1	131	23	.31	8.0	41	183	.86	22.0	0.091	2.3	8.50	SPR	C	Z
0.578	14.68	4116	1.50	38.1	.470	11.9	12	2.1	.81	21	9.8	44	.54	13.7	0.054	1.4	9.00	SPR	C	Z
0.578	14.68	S-887	1.53	38.9	.398	10.1	94	16	.39	10	37	164	.86	21.7	0.090	2.3	9.50	SST	CG	N
0.578	14.68	S-199	1.56	39.7	.488	12.4	6.2	1.1	.93	24	5.7	26	.38	9.7	0.045	1.1	7.50	SST	C	N
0.578	14.68	4321	1.63	41.3	.470	11.9	11	1.9	.92	23	9.8	44	.54	13.7	0.054	1.4	10.0	SPR	CG	Z
0.578	14.68	12209	1.63	41.3	.434	11.0	37	6.5	.58	15	22	97	.72	18.3	0.072	1.8	10.0	SPR	CG	Z
0.578	14.68	NN-56	1.69	42.8	.398	10.1	80	14	.46	12	37	164	.99	25.1	0.090	2.3	11.0	SST	CG	N
0.578	14.68	2797	1.75	44.5	.338	8.6	443	78	.20	5.0	88	390	1.08	27.4	0.120	3.0	9.00	SPR	CG	Z
0.578	14.68	3870	1.81	46.0	.488	12.4	4.1	.72	1.3	33	5.3	24	.52	13.1	0.045	1.1	11.5	SPR	CG	Z
0.578	14.68	10858	1.81	46.0	.448	11.4	17	3.0	.92	23	16	71	.76	19.4	0.065	1.7	11.8	SST	CG	N
0.578	14.68	4230	1.88	47.6	.474	12.0	8.3	1.4	1.1	27	8.8	39	.61	15.5	0.052	1.3	10.8	SPR	C	Z
0.578	14.68	12634	1.97	50.0	.506	12.9	1.9	.33	1.6	40	3.0	13	.40	10.1	0.036	0.9	10.0	MW	C	Z
0.578	14.68	12249	2.00	50.8	.484	12.3	4.3	.75	1.4	35	5.9	26	.61	15.5	0.047	1.2	13.0	SPR	CG	Z
0.578	14.68	3317	2.00	50.8	.428	10.9	36	6.3	.68	17	24	109	.90	22.9	0.075	1.9	12.0	SPR	CG	Z
0.578	14.68	M-92	2.00	50.8	.266	6.8	1259	220	.13	3.4	170	754	1.72	43.6	0.156	4.0	11.0	SPR	CG	N
0.578	14.68	11888	2.03	51.6	.430	10.9	34	5.9	.70	18	24	105	.89	22.6	0.074	1.9	12.0	SPR	CG	N
0.578	14.68	12231	2.03	51.6	.428	10.9	40	7.0	.62	16	24	109	.83	21.0	0.075	1.9	11.0	SPR	CG	Z
0.578	14.68	11317	2.13	54.0	.378	9.6	110	19	.49	13	54	240	1.40	35.6	0.100	2.5	14.0	SPR	CG	Z
0.578	14.68	10382	2.25	57.2	.496	12.6	3.5	.61	1.3	34	4.7	21	.43	10.9	0.041	1.0	9.50	SPR	C	Z
0.578	14.68	12299	2.28	57.9	.418	10.6	37	6.4	.80	20	30	131	1.20	30.5	0.080	2.0	15.0	SPR	CG	Z
0.578	14.68	12214	2.34	59.5	.478	12.1	6.1	1.1	1.3	33	7.8	35	.60	15.2	0.050	1.3	12.0	SPR	CG	Z
0.578	14.68	3200	2.38	60.3	.518	13.2	.55	.10	1.9	48	1.1	4.7	.47	12.0	0.030	0.8	14.8	MW	C	Z
0.578	14.68	10419	2.38	60.3	.444	11.3	21	3.6	.90	23	19	82	.91	23.0	0.067	1.7	12.5	SPR	C	Z
0.578	14.68	S-49	2.50	63.5	.396	10.1	53	9.3	.72	18	38	170	1.55	39.3	0.091	2.3	16.0	SST	C	N
0.578	14.68	10473	2.56	65.1	.454	11.5	9.7	1.7	1.4	37	14	62	1.12	28.3	0.062	1.6	18.0	SPR	CG	Z
0.578	14.68	12063	2.59	65.9	.482	12.2	5.1	.90	1.4	37	7.4	33	.58	14.6	0.048	1.2	12.0	SPR	CG	GI
0.578	14.68	S-1453	2.63	66.7	.434	11.0	22	3.9	.92	23	20	90	.99	25.1	0.072	1.8	13.8	SST	CG	N
0.578	14.68	11313	2.66	67.5	.434	11.0	23	4.1	.93	24	22	97	1.06	27.0	0.072	1.8	14.8	SPR	CG	Z
0.578	14.68	S-472	3.13	79.4	.516	13.1	.61	.11	2.7	68	1.6	7.3	.45	11.4	0.031	0.8	13.5	SST	C	N
0.578	14.68	2829	3.13	79.4	.484	12.3	1.6	.28	1.6	40	2.5	11	1.54	39.1	0.047	1.2	31.8	HD	C	Z
0.578	14.68	10490	3.16	80.2	.422	10.7	28	5.0	.97	25	27	122	1.33	33.7	0.078	2.0	17.0	SPR	CG	BO
0.578	14.68	10306	3.31	84.1	.368	9.3	86	15	.72	18	62	276	2.23	56.7	0.105	2.7	21.3	SPR	CG	Z
0.578	14.68	10987	3.75	95.3	.368	9.3	90	16	.69	17	62	276	2.13	54.0	0.105	2.7	20.3	HD	CG	Z
0.578	14.68	10965	3.75	95.3	.358	9.1	124	22	.55	14	69	305	2.03	51.6	0.110	2.8	18.5	HD	CG	Z
0.578	14.68	S-3041	4.75	120.7	.454	11.5	4.6	.78	2.7	69	12	54	2.05	52.0	0.062	1.6	32.0	SST	C	N
0.578	14.68	3345	5.00	127.0	.438	11.1	11	1.9	1.8	46	20	89	1.82	46.2	0.070	1.8	26.0	SPR	CG	Z
0.578	14.68	12296	5.38	136.5	.462	11.7	5.4	.94	2.3	57	12	54	1.42	36.1	0.058	1.5	23.5	SPR	C	Z
0.578	14.68	10087	5.38	136.5	.454	11.5	7.0	1.2	2.1	53	15	66	1.55	39.4	0.062	1.6	24.0	HD	C	N
0.578	14.68	12081	5.50	139.7	.454	11.5	6.2	1.1	2.4	61	15	66	1.67	42.5	0.062	1.6	27.0	SPR	CG	Z
0.578	14.68	4187	7.50	190.5	.458	11.6	4.2	.73	3.2	81	13	60	2.10	53.3	0.060	1.5	34.0	SPR	C	BO
0.578	14.68	S-3043	7.63	193.7	.454	11.5	4.2	.74	3.3	84	14	62	2.17	55.1	0.062	1.6	34.0	SST	C	N
0.578	14.68	4016	23.5	596.9	.408	10.4	5.7	1.0	6.2	156	35	157	9.56	242.9	0.085	2.2	111.5	SPR	C	Z
0.590	14.99	12524	1.50	38.1	.386	9.8	255	45	.22	5.6	56	250	.74	18.8	0.102	2.6	7.25	SPR	CG	N
0.593	15.06	3789	.44	11.1	.497	12.6	13	2.4	.17	4.4	2.3	10	.26	6.7	0.048	1.2	5.50	SPR	CG	Z
0.593	15.06	N-51	.47	11.9	.499	12.7	12	2.2	.21	5.3	2.6	11	.26	6.6	0.047	1.2	5.50	SPR	CG	N
0.593	15.06	10334	.50	12.7	.459	11.7	199	35	.09	2.3	18	80	.27	6.8	0.067	1.7	3.00	SPR	C	Z
0.593	15.06	A-47	.53	13.5	.393	10.0	800	140	.07	1.7	53	235	.35	8.9	0.100	2.5	3.50	SPR	CG	GI
0.593	15.06	NN-92	.56	14.3	.523	13.3	2.4	.42	.30	7.6	.72	3.2	.26	6.7	0.035	0.9	6.50	SST	C	N
0.593	15.06	11341	.56	14.3	.503	12.8	14	2.5	.37	9.4	5.2	23	.19	4.9	0.045	1.1	4.25	SST	CG	N
0.593	15.06	I-79	.56	14.3	.483	12.3	42	7.4	.24	6.1	10									



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.593	15.06	I-46	.81	20.6	.531	13.5	2.4	.41	.63	16	1.5	6.7	.18	4.5	0.031	0.8	4.75	SST	C	N
0.593	15.06	3547	.84	21.4	.463	11.8	44	7.6	.38	9.6	17	74	.39	9.9	0.065	1.7	6.00	HD	CG	GI
0.593	15.06	2940	.84	21.4	.459	11.7	57	10	.32	8.1	18	80	.37	9.4	0.067	1.7	5.50	SPR	CG	Z
0.593	15.06	3840	.84	21.4	.449	11.4	78	14	.27	6.9	21	94	.40	10.1	0.072	1.8	5.50	SPR	CG	Z
0.593	15.06	12277	.88	22.2	.513	13.0	4.4	.76	.60	15	2.6	12	.28	7.1	0.040	1.0	7.00	SPR	CG	Z
0.593	15.06	S-1393	.88	22.2	.469	11.9	35	6.2	.38	9.8	14	60	.34	8.7	0.062	1.6	5.50	SST	CG	N
0.593	15.06	B-98	.88	22.2	.467	11.9	51	8.9	.30	7.6	15	67	.32	8.0	0.063	1.6	5.00	SPR	CG	Z
0.593	15.06	3918	.88	22.2	.449	11.4	84	15	.25	6.4	21	94	.38	9.6	0.072	1.8	5.25	HD	CG	Z
0.593	15.06	11196	.91	23.0	.463	11.8	48	8.3	.33	8.3	16	69	.34	8.7	0.065	1.7	5.25	SST	CG	N
0.593	15.06	12689	.92	23.4	.451	11.5	73	13	.39	9.8	28	126	.39	9.9	0.071	1.8	5.50	MW	CG	Z
0.593	15.06	S-3096	.94	23.8	.473	12.0	31	5.4	.40	10	12	55	.39	9.9	0.060	1.5	5.50	SST	C	N
0.593	15.06	3091	.94	23.8	.469	11.9	28	4.8	.50	13	14	61	.44	11.2	0.062	1.6	7.00	SPR	CG	Z
0.593	15.06	1923	.97	24.6	.289	7.3	2982	522	.05	1.3	156	693	.76	19.3	0.152	3.9	5.00	SPR	CG	Z
0.593	15.06	A13-58	1.00	25.4	.531	13.5	1.9	.33	.83	21	1.6	7.0	.17	4.3	0.031	0.8	5.50	SST	CG	N
0.593	15.06	10366	1.00	25.4	.519	13.2	4.5	.78	.75	19	3.3	15	.24	6.1	0.037	0.9	5.50	SPR	C	Z
0.593	15.06	GG-42	1.00	25.4	.453	11.5	61	11	.30	7.6	18	81	.39	9.8	0.070	1.8	5.50	SST	CG	N
0.593	15.06	BB-65	1.00	25.4	.443	11.3	93	16	.26	6.5	24	106	.41	10.5	0.075	1.9	5.50	SPR	CG	Z
0.593	15.06	A11-66	1.03	26.2	.531	13.5	1.9	.33	.86	22	1.6	7.3	.17	4.3	0.031	0.8	5.50	SST	CG	N
0.593	15.06	S-375	1.03	26.2	.469	11.9	25	4.3	.55	14	14	60	.43	11.0	0.062	1.6	7.00	SST	CG	N
0.593	15.06	K-46	1.13	28.6	.469	11.9	25	4.3	.55	14	14	60	.43	11.0	0.062	1.6	7.00	SST	CG	N
0.593	15.06	3536	1.13	28.6	.467	11.9	30	5.3	.68	17	21	93	.44	11.2	0.063	1.6	7.00	MW	CG	Z
0.593	15.06	3320	1.13	28.6	.449	11.4	43	7.6	.49	12	21	94	.60	15.2	0.072	1.8	8.25	HD	CG	Z
0.593	15.06	S-1362	1.13	28.6	.433	11.0	63	11	.43	11	27	120	.64	16.3	0.080	2.0	8.00	SST	CG	N
0.593	15.06	4297	1.13	28.6	.411	10.4	148	26	.27	6.9	40	179	.75	19.1	0.091	2.3	7.25	SPR	C	Z
0.593	15.06	S-1356	1.16	29.4	.433	11.0	76	13	.36	9.0	27	120	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.593	15.06	10174	1.19	30.2	.499	12.7	8.6	1.5	.79	20	6.8	30	.38	9.6	0.047	1.2	7.00	SPR	C	Z
0.593	15.06	B12-65	1.19	30.2	.457	11.6	30	5.3	.58	15	17	78	.61	15.5	0.068	1.7	9.00	SPR	CG	Z
0.593	15.06	G-60A	1.19	30.2	.433	11.0	47	8.3	.39	9.9	18	82	.80	20.3	0.080	2.0	10.0	SST	CG	N
0.593	15.06	S-295	1.19	30.2	.427	10.8	65	11	.44	11	29	128	.75	19.0	0.083	2.1	9.00	SST	CG	N
0.593	15.06	11226	1.19	30.2	.411	10.4	111	19	.36	9.2	40	179	.82	20.8	0.091	2.3	9.00	SPR	CG	Z
0.593	15.06	Q-35	1.22	31.0	.357	9.1	355	62	.21	5.3	75	332	1.00	25.5	0.118	3.0	8.50	SST	CG	N
0.593	15.06	12560	1.25	31.8	.531	13.5	1.6	.28	1.0	26	1.7	7.5	.22	5.5	0.031	0.8	6.00	SST	C	N
0.593	15.06	2719	1.25	31.8	.517	13.1	3.9	.68	.97	25	3.8	17	.29	7.2	0.038	1.0	6.50	MW	C	Z
0.593	15.06	4247	1.25	31.8	.505	12.8	6.5	1.1	.86	22	5.6	25	.35	8.9	0.044	1.1	7.00	SPR	C	Z
0.593	15.06	V-28	1.25	31.8	.449	11.4	68	12	.29	7.4	20	88	.40	10.1	0.072	1.8	5.50	SST	CG	N
0.593	15.06	KK-53	1.25	31.8	.433	11.0	62	11	.46	12	29	128	.72	18.3	0.080	2.0	9.00	SPR	CG	Z
0.593	15.06	2890	1.28	32.5	.423	10.7	95	17	.36	9.2	34	153	.68	17.3	0.085	2.2	8.00	SPR	CG	Z
0.593	15.06	10531	1.34	34.1	.469	11.9	19	3.3	.75	19	14	63	.59	15.0	0.062	1.6	9.50	SPR	CG	Z
0.593	15.06	S-237	1.38	34.9	.459	11.7	23	4.0	.74	19	17	76	.64	16.2	0.067	1.7	9.50	SST	CG	N
0.593	15.06	2686	1.41	35.7	.383	9.7	200	35	.30	7.7	61	270	1.00	25.3	0.105	2.7	9.50	HD	CG	Z
0.593	15.06	3228	1.44	36.5	.433	11.0	67	12	.43	11	29	128	.76	19.3	0.080	2.0	8.50	SPR	C	Z
0.593	15.06	10608	1.47	37.3	.463	11.8	25	4.4	.66	17	17	74	.59	14.9	0.065	1.7	9.00	SPR	CG	N
0.593	15.06	I-88	1.50	38.1	.449	11.4	34	6.0	.62	16	21	94	.72	18.3	0.072	1.8	10.0	HD	CG	Z
0.593	15.06	1691	1.50	38.1	.413	10.5	93	16	.42	11	39	173	.90	22.9	0.090	2.3	10.0	SPR	CG	Z
0.593	15.06	S-428	1.56	39.7	.501	12.7	6.1	1.1	.98	25	6.0	27	.35	8.9	0.046	1.2	7.50	SST	CG	N
0.593	15.06	S-412	1.56	39.7	.483	12.3	10	1.8	.91	23	9.5	42	.50	12.6	0.055	1.4	9.00	SST	CG	N
0.593	15.06	Q-58	1.56	39.7	.465	11.8	22	3.8	.73	18	16	70	.67	17.1	0.064	1.6	9.50	SPR	C	N
0.593	15.06	10113	1.56	39.7	.323	8.2	710	124	.16	4.1	116	515	1.22	30.9	0.135	3.4	9.00	SPR	CG	Z
0.593	15.06	3060	1.63	41.3	.513	13.0	2.4	.42	1.2	30	2.9	13	.44	11.2	0.040	1.0	11.0	SPR	CG	Z
0.593	15.06	S-856	1.63	41.3	.485	12.3	6.0	1.1	.90	23	5.4	24	.73	18.5	0.054	1.4	13.5	SST	CG	N
0.593	15.06	3268	1.63	41.3	.459	11.7	23	4.1	.77	20	18	80	.70	17.9	0.067	1.7	10.5	SPR	CG	Z
0.593	15.06	10030	1.63	41.3	.449	11.4	34	6.0	.62	16	21	94	.72	18.3	0.072	1.8	10.0	HD	CG	Z
0.593	15.06	10717	1.63	41.3	.433	11.0	47	8.3	.61	16	29	128	.90	22.9	0.080	2.0	11.3	SPR	CG	GI
0.593	15.06	3057	1.63	41.3	.383	9.7	215	38	.28	7.2	61	270	.95	24.0	0.105	2.7	9.00	SPR	CG	Z
0.593	15.06	A11-49	1.72	43.6	.457	11.6	28	4.9	.68	17	19	84	.66	16.7	0.068	1.7	9.75	SPR	CG	GI
0.593	15.06	JJ-83	1.75	44.5	.501	12.7	2.4	.43	.97	25	2.4	11	.78	19.9	0.046	1.2	16.0	SST	C	N
0.593	15.06	3500	1.75	44.5	.469	11.9	18	3.1	.81	21	14	64	.62	15.7	0.062	1.6	10.0	SPR	CG	Z
0.593	15.06	12186	1.78	45.2	.493	12.5	6.1	1.1	1.2	30	7.1	32	.61	15.6	0.050	1.3	11.3	SPR	C	



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.593	15.06	11729	3.00	76.2	.433	11.0	27	4.8	1.1	27	29	128	1.44	36.6	0.080	2.0	18.0	SPR	CG	GI
0.593	15.06	3090	3.00	76.2	.383	9.7	90	16	.68	17	61	270	1.97	50.0	0.105	2.7	18.8	SPR	CG	Z
0.593	15.06	11795	3.03	77.0	.451	11.5	15	2.6	1.3	34	20	90	1.35	34.3	0.071	1.8	19.0	SPR	CG	Z
0.593	15.06	2772	3.13	79.4	.499	12.7	2.0	.34	2.0	51	3.9	17	1.13	28.7	0.047	1.2	24.0	HD	CG	Z
0.593	15.06	3950	3.50	88.9	.449	11.4	27	4.8	.78	20	21	94	.86	21.9	0.072	1.8	12.0	SPR	CG	Z
0.593	15.06	11663	3.50	88.9	.445	11.3	21	3.6	1.1	28	23	102	1.26	32.0	0.074	1.9	17.0	SPR	CG	Z
0.593	15.06	10560	3.50	88.9	.393	10.0	58	10	.91	23	53	235	2.28	57.8	0.100	2.5	22.8	SPR	CG	Z
0.593	15.06	10228	4.00	101.6	.527	13.4	.49	.08	3.2	82	1.6	7.0	.76	19.3	0.033	0.8	22.0	SPR	C	Z
0.593	15.06	1611	4.00	101.6	.383	9.7	88	15	.69	17	61	270	2.00	50.7	0.105	2.7	19.0	SPR	CG	Z
0.593	15.06	10636	4.00	101.6	.367	9.3	88	15	.82	21	72	322	2.94	74.6	0.113	2.9	26.0	SPR	CG	Z
0.593	15.06	11769	4.31	109.5	.433	11.0	22	3.8	1.3	34	29	128	1.76	44.7	0.080	2.0	22.0	SPR	CG	Z
0.593	15.06	1815	5.38	136.5	.411	10.4	33	5.8	1.7	43	56	250	2.32	59.0	0.091	2.3	25.5	MW	CG	Z
0.593	15.06	1521	5.50	139.7	.411	10.4	31	5.5	1.3	33	40	179	2.46	62.4	0.091	2.3	27.0	HD	CG	Z
0.593	15.06	12178	5.75	146.1	.413	10.5	24	4.2	1.6	41	39	173	2.97	75.4	0.090	2.3	33.0	SPR	CG	Z
0.593	15.06	10681	6.00	152.4	.411	10.4	19	3.3	2.1	53	40	176	3.91	99.4	0.091	2.3	43.0	SPR	CG	Z
0.593	15.06	2902	6.25	158.8	.423	10.7	19	3.3	1.8	46	34	153	2.72	69.1	0.085	2.2	32.0	SPR	CG	Z
0.600	15.24	71711	.50	12.7	.510	13.0	23	4.1	.34	8.7	7.9	35	.16	4.0	0.045	1.1	3.50	MW	CG	N
0.600	15.24	71711S	.50	12.7	.510	13.0	20	3.5	.28	7.1	5.5	25	.16	4.0	0.045	1.1	3.50	SST	CG	N
0.600	15.24	71712	.63	16.0	.510	13.0	18	3.2	.45	12	8.2	36	.17	4.4	0.045	1.1	3.88	MW	CG	N
0.600	15.24	71712S	.63	16.0	.510	13.0	15	2.7	.36	9.2	5.5	25	.17	4.4	0.045	1.1	3.88	SST	CG	N
0.600	15.24	71729	.63	16.0	.502	12.8	28	4.9	.38	9.6	11	47	.18	4.7	0.049	1.2	3.75	MW	CG	N
0.600	15.24	71729S	.63	16.0	.502	12.8	24	4.2	.30	7.6	7.1	32	.18	4.7	0.049	1.2	3.75	SST	CG	N
0.600	15.24	71741	.63	16.0	.490	12.4	40	7.0	.35	8.8	14	62	.22	5.6	0.055	1.4	4.00	MW	CG	N
0.600	15.24	71741S	.63	16.0	.490	12.4	34	6.0	.28	7.0	9.4	42	.22	5.6	0.055	1.4	4.00	SST	CG	N
0.600	15.24	71753	.63	16.0	.482	12.2	53	9.3	.32	8.1	17	76	.24	6.2	0.059	1.5	4.13	MW	CG	N
0.600	15.24	71753S	.63	16.0	.482	12.2	45	7.9	.26	6.5	12	51	.24	6.2	0.059	1.5	4.13	SST	CG	N
0.600	15.24	71765	.63	16.0	.474	12.0	63	11	.33	8.4	21	92	.28	7.0	0.063	1.6	4.38	MW	CG	N
0.600	15.24	71765S	.63	16.0	.474	12.0	54	9.4	.26	6.7	14	62	.28	7.0	0.063	1.6	4.38	SST	CG	N
0.600	15.24	71779	.63	16.0	.466	11.8	80	14	.31	7.9	25	110	.29	7.4	0.067	1.7	4.38	MW	CG	N
0.600	15.24	71779S	.63	16.0	.466	11.8	68	12	.25	6.3	17	75	.29	7.4	0.067	1.7	4.38	SST	CG	N
0.600	15.24	71791	.63	16.0	.456	11.6	109	19	.27	6.8	29	130	.32	8.0	0.072	1.8	4.38	MW	CG	N
0.600	15.24	71791S	.63	16.0	.456	11.6	92	16	.21	5.4	20	87	.32	8.0	0.072	1.8	4.38	SST	CG	N
0.600	15.24	71803	.63	16.0	.438	11.1	203	36	.20	5.2	41	184	.33	8.5	0.081	2.1	4.13	MW	CG	N
0.600	15.24	71803S	.63	16.0	.438	11.1	173	30	.16	4.1	28	123	.33	8.5	0.081	2.1	4.13	SST	CG	N



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.600	15.24	71715	1.00	25.4	.510	13.0	9.9	1.7	.75	19	7.4	33	.25	6.3	0.045	1.1	5.50	MW	CG	Z
0.600	15.24	71715S	1.00	25.4	.510	13.0	8.7	1.5	.64	16	5.5	25	.24	6.1	0.045	1.1	5.38	SST	CG	N
0.600	15.24	71732	1.00	25.4	.502	12.8	16	2.8	.65	17	11	47	.25	6.4	0.049	1.2	5.13	MW	CG	N
0.600	15.24	71732S	1.00	25.4	.502	12.8	14	2.4	.52	13	7.1	32	.25	6.4	0.049	1.2	5.13	SST	CG	N
0.600	15.24	71744	1.00	25.4	.490	12.4	24	4.2	.58	15	14	62	.30	7.5	0.055	1.4	5.38	MW	CG	N
0.600	15.24	71744S	1.00	25.4	.490	12.4	20	3.6	.46	12	9.4	42	.30	7.5	0.055	1.4	5.38	SST	CG	N
0.600	15.24	71756	1.00	25.4	.482	12.2	30	5.3	.56	14	17	76	.33	8.4	0.059	1.5	5.63	MW	CG	N
0.600	15.24	71756S	1.00	25.4	.482	12.2	26	4.5	.45	11	12	51	.33	8.4	0.059	1.5	5.63	SST	CG	N
0.600	15.24	71768	1.00	25.4	.474	12.0	38	6.7	.55	14	21	92	.37	9.4	0.063	1.6	5.88	MW	CG	N
0.600	15.24	71768S	1.00	25.4	.474	12.0	32	5.7	.43	11	14	62	.37	9.4	0.063	1.6	5.88	SST	CG	N
0.600	15.24	71782	1.00	25.4	.466	11.8	45	7.9	.55	14	25	110	.42	10.6	0.067	1.7	6.25	MW	CG	N
0.600	15.24	71782S	1.00	25.4	.466	11.8	38	6.7	.44	11	17	75	.42	10.6	0.067	1.7	6.25	SST	CG	N
0.600	15.24	71794	1.00	25.4	.456	11.6	55	9.6	.51	13	28	126	.49	12.3	0.072	1.8	6.75	MW	CG	N
0.600	15.24	71794S	1.00	25.4	.456	11.6	47	8.2	.42	11	20	87	.49	12.3	0.072	1.8	6.75	SST	CG	N
0.600	15.24	71806	1.00	25.4	.438	11.1	112	20	.37	9.4	41	184	.49	12.3	0.081	2.1	6.00	MW	CG	N
0.600	15.24	71806S	1.00	25.4	.438	11.1	95	17	.29	7.4	28	123	.49	12.3	0.081	2.1	6.00	SST	CG	N
0.600	15.24	71822	1.00	25.4	.430	10.9	142	25	.33	8.5	48	211	.50	12.7	0.085	2.2	5.88	MW	CG	N
0.600	15.24	71822S	1.00	25.4	.430	10.9	121	21	.26	6.7	32	142	.50	12.7	0.085	2.2	5.88	SST	CG	N
0.600	15.24	71837	1.00	25.4	.416	10.6	202	35	.28	7.2	57	256	.54	13.7	0.092	2.3	5.88	MW	CG	N
0.600	15.24	71837S	1.00	25.4	.416	10.6	172	30	.22	5.6	38	169	.54	13.7	0.092	2.3	5.88	SST	CG	N
0.600	15.24	71852	1.00	25.4	.404	10.3	267	47	.26	6.6	69	307	.58	14.6	0.098	2.5	5.88	MW	CG	N
0.600	15.24	71852S	1.00	25.4	.404	10.3	227	40	.20	5.1	46	203	.58	14.6	0.098	2.5	5.88	SST	CG	N
0.600	15.24	71716	1.25	31.8	.510	13.0	8.0	1.4	.97	25	7.8	34	.28	7.1	0.045	1.1	6.25	MW	CG	N
0.600	15.24	71716S	1.25	31.8	.510	13.0	6.8	1.2	.81	21	5.5	25	.28	7.1	0.045	1.1	6.25	SST	CG	N
0.600	15.24	71733	1.25	31.8	.502	12.8	13	2.3	.82	21	11	47	.29	7.3	0.049	1.2	5.88	MW	CG	N
0.600	15.24	71733S	1.25	31.8	.502	12.8	11	1.9	.65	17	7.1	32	.29	7.3	0.049	1.2	5.88	SST	CG	N
0.600	15.24	71745	1.25	31.8	.490	12.4	19	3.2	.75	19	14	62	.35	8.9	0.055	1.4	6.38	MW	CG	N
0.600	15.24	71745S	1.25	31.8	.490	12.4	16	2.8	.60	15	9.4	42	.35	8.9	0.055	1.4	6.38	SST	CG	N
0.600	15.24	71757	1.25	31.8	.482	12.2	24	4.2	.71	18	17	76	.39	9.9	0.059	1.5	6.63	MW	CG	N
0.600	15.24	71757S	1.25	31.8	.482	12.2	20	3.6	.57	14	12	51	.39	9.9	0.059	1.5	6.63	SST	CG	N
0.600	15.24	71769	1.25	31.8	.474	12.0	31	5.3	.68	17	21	92	.43	10.8	0.063	1.6	6.75	MW	CG	N
0.600	15.24	71769S	1.25	31.8	.474	12.0	26	4.5	.54	14	14	62	.43	10.8	0.063	1.6	6.75	SST	CG	N
0.600	15.24	71783	1.25	31.8	.466	11.8	35	6.1	.71	18	25	110	.50	12.8	0.067					



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.600	15.24	71785	1.75	44.5	.466	11.8	24	4.1	1.1	27	25	110	.68	17.2	0.067	1.7	10.1	MW	CG	N
0.600	15.24	71785S	1.75	44.5	.466	11.8	20	3.5	.84	21	17	75	.68	17.2	0.067	1.7	10.1	SST	CG	N
0.600	15.24	71797	1.75	44.5	.456	11.6	30	5.3	.98	25	29	130	.77	19.7	0.072	1.8	10.8	MW	CG	N
0.600	15.24	71797S	1.75	44.5	.456	11.6	26	4.5	.77	20	20	87	.77	19.7	0.072	1.8	10.8	SST	CG	N
0.600	15.24	71809	1.75	44.5	.438	11.1	59	10	.70	18	41	184	.77	19.5	0.081	2.1	9.50	MW	CG	N
0.600	15.24	71809S	1.75	44.5	.438	11.1	50	8.8	.55	14	28	123	.77	19.5	0.081	2.1	9.50	SST	CG	N
0.600	15.24	71825	1.75	44.5	.430	10.9	75	13	.64	16	48	211	.80	20.2	0.085	2.2	9.38	MW	CG	N
0.600	15.24	71825S	1.75	44.5	.430	10.9	64	11	.50	13	32	142	.80	20.2	0.085	2.2	9.38	SST	CG	N
0.600	15.24	71840	1.75	44.5	.416	10.6	105	18	.55	14	57	256	.87	22.2	0.092	2.3	9.50	MW	CG	N
0.600	15.24	71840S	1.75	44.5	.416	10.6	90	16	.43	11	38	169	.87	22.2	0.092	2.3	9.50	SST	CG	N
0.600	15.24	71855	1.75	44.5	.404	10.3	138	24	.50	13	69	307	.94	24.0	0.098	2.5	9.63	MW	CG	N
0.600	15.24	71855S	1.75	44.5	.404	10.3	118	21	.39	9.9	46	203	.94	24.0	0.098	2.5	9.63	SST	CG	N
0.600	15.24	71721	2.00	50.8	.510	13.0	5.3	.92	1.6	39	8.2	36	.38	9.7	0.045	1.1	8.50	MW	CG	N
0.600	15.24	71721S	2.00	50.8	.510	13.0	4.5	.79	1.2	31	5.5	25	.38	9.7	0.045	1.1	8.50	SST	CG	N
0.600	15.24	71736	2.00	50.8	.502	12.8	7.6	1.3	1.4	35	11	47	.42	10.6	0.049	1.2	8.50	MW	CG	N
0.600	15.24	71736S	2.00	50.8	.502	12.8	6.5	1.1	1.1	28	7.1	32	.42	10.6	0.049	1.2	8.50	SST	CG	N
0.600	15.24	71748	2.00	50.8	.490	12.4	11	2.0	1.2	32	14	62	.51	12.9	0.055	1.4	9.25	MW	CG	N
0.600	15.24	71748S	2.00	50.8	.490	12.4	9.5	1.7	.99	25	9.4	42	.51	12.9	0.055	1.4	9.25	SST	CG	N
0.600	15.24	71760	2.00	50.8	.482	12.2	14	2.5	1.2	31	17	76	.58	14.6	0.059	1.5	9.75	MW	CG	N
0.600	15.24	71760S	2.00	50.8	.482	12.2	12	2.1	.96	24	12	51	.58	14.6	0.059	1.5	9.75	SST	CG	N
0.600	15.24	71772	2.00	50.8	.474	12.0	18	3.1	1.2	30	21	92	.65	16.4	0.063	1.6	10.3	MW	CG	N
0.600	15.24	71772S	2.00	50.8	.474	12.0	15	2.6	.93	24	14	62	.65	16.4	0.063	1.6	10.3	SST	CG	N
0.600	15.24	71786	2.00	50.8	.466	11.8	21	3.7	1.2	30	25	110	.75	18.9	0.067	1.7	11.1	MW	CG	N
0.600	15.24	71786S	2.00	50.8	.466	11.8	18	3.1	.94	24	17	75	.75	18.9	0.067	1.7	11.1	SST	CG	N
0.600	15.24	71798	2.00	50.8	.456	11.6	27	4.7	1.1	28	29	130	.85	21.5	0.072	1.8	11.8	MW	CG	N
0.600	15.24	71798S	2.00	50.8	.456	11.6	23	4.0	.86	22	20	87	.85	21.5	0.072	1.8	11.8	SST	CG	N
0.600	15.24	71810	2.00	50.8	.438	11.1	51	8.9	.81	21	41	184	.87	22.1	0.081	2.1	10.8	MW	CG	N
0.600	15.24	71810S	2.00	50.8	.438	11.1	43	7.6	.64	16	28	123	.87	22.1	0.081	2.1	10.8	SST	CG	N
0.600	15.24	71826	2.00	50.8	.430	10.9	65	11	.74	19	48	211	.89	22.7	0.085	2.2	10.5	MW	CG	N
0.600	15.24	71826S	2.00	50.8	.430	10.9	55	9.6	.58	15	32	142	.89	22.7	0.085	2.2	10.5	SST	CG	N
0.600	15.24	71841	2.00	50.8	.416	10.6	91	16	.63	16	57	256	.98	24.8	0.092	2.3	10.6	MW	CG	N
0.600	15.24	71841S	2.00	50.8	.416	10.6	77	14	.49	13	38	169	.98	24.8	0.092	2.3	10.6	SST	CG	N
0.600	15.24	71856	2.00	50.8	.404	10.3	119	21	.58	15	69	307	1.05							



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.600	15.24	71739	2.75	69.9	.502	12.8	5.3	.93	2.0	51	11	47	.56	14.2	0.049	1.2	11.4	MW	CG	N
0.600	15.24	71739S	2.75	69.9	.502	12.8	4.5	.79	1.6	40	7.1	32	.56	14.2	0.049	1.2	11.4	SST	CG	N
0.600	15.24	71751	2.75	69.9	.490	12.4	8.0	1.4	1.7	44	14	62	.67	16.9	0.055	1.4	12.1	MW	CG	N
0.600	15.24	71751S	2.75	69.9	.490	12.4	6.8	1.2	1.4	35	9.4	42	.67	16.9	0.055	1.4	12.1	SST	CG	N
0.600	15.24	71763	2.75	69.9	.482	12.2	9.8	1.7	1.8	44	17	76	.78	19.9	0.059	1.5	13.3	MW	CG	N
0.600	15.24	71763S	2.75	69.9	.482	12.2	8.3	1.5	1.4	35	12	51	.78	19.9	0.059	1.5	13.3	SST	CG	N
0.600	15.24	71775	2.75	69.9	.474	12.0	13	2.3	1.6	41	21	92	.83	21.2	0.063	1.6	13.3	MW	CG	N
0.600	15.24	71775S	2.75	69.9	.474	12.0	11	1.9	1.3	32	14	62	.83	21.2	0.063	1.6	13.3	SST	CG	N
0.600	15.24	71789	2.75	69.9	.466	11.8	15	2.6	1.6	42	25	110	.99	25.1	0.067	1.7	14.8	MW	CG	N
0.600	15.24	71789S	2.75	69.9	.466	11.8	13	2.2	1.3	33	17	75	.99	25.1	0.067	1.7	14.8	SST	CG	N
0.600	15.24	71801	2.75	69.9	.456	11.6	20	3.5	1.5	37	29	130	1.09	27.7	0.072	1.8	15.1	MW	CG	N
0.600	15.24	71801S	2.75	69.9	.456	11.6	17	3.0	1.2	29	20	87	1.09	27.7	0.072	1.8	15.1	SST	CG	N
0.600	15.24	71813	2.75	69.9	.438	11.1	36	6.3	1.1	29	41	184	1.15	29.3	0.081	2.1	14.3	MW	CG	N
0.600	15.24	71813S	2.75	69.9	.438	11.1	31	5.4	.90	23	28	123	1.15	29.3	0.081	2.1	14.3	SST	CG	N
0.600	15.24	71829	2.75	69.9	.430	10.9	46	8.0	1.0	26	48	211	1.19	30.2	0.085	2.2	14.0	MW	CG	N
0.600	15.24	71829S	2.75	69.9	.430	10.9	39	6.8	.82	21	32	142	1.19	30.2	0.085	2.2	14.0	SST	CG	N
0.600	15.24	71844	2.75	69.9	.416	10.6	64	11	.89	23	57	256	1.31	33.3	0.092	2.3	14.3	MW	CG	N
0.600	15.24	71844S	2.75	69.9	.416	10.6	55	9.6	.70	18	38	169	1.31	33.3	0.092	2.3	14.3	SST	CG	N
0.600	15.24	71859	2.75	69.9	.404	10.3	84	15	.82	21	69	307	1.42	36.1	0.098	2.5	14.5	MW	CG	N
0.600	15.24	71859S	2.75	69.9	.404	10.3	71	13	.64	16	46	203	1.42	36.1	0.098	2.5	14.5	SST	CG	N
0.600	15.24	71725	3.00	76.2	.510	13.0	3.3	.58	2.4	62	8.0	36	.56	14.3	0.045	1.1	12.5	MW	CG	N
0.600	15.24	71725S	3.00	76.2	.510	13.0	2.8	.49	2.0	50	5.5	25	.56	14.3	0.045	1.1	12.5	SST	CG	N
0.600	15.24	71740	3.00	76.2	.502	12.8	4.8	.84	2.2	56	11	47	.60	15.2	0.049	1.2	12.3	MW	CG	N
0.600	15.24	71740S	3.00	76.2	.502	12.8	4.1	.72	1.7	44	7.1	32	.60	15.2	0.049	1.2	12.3	SST	CG	N
0.600	15.24	71752	3.00	76.2	.490	12.4	7.3	1.3	1.9	48	14	62	.72	18.3	0.055	1.4	13.1	MW	CG	N
0.600	15.24	71752S	3.00	76.2	.490	12.4	6.2	1.1	1.5	38	9.4	42	.72	18.3	0.055	1.4	13.1	SST	CG	N
0.600	15.24	71764	3.00	76.2	.482	12.2	9.0	1.6	1.9	48	17	76	.84	21.4	0.059	1.5	14.3	MW	CG	N
0.600	15.24	71764S	3.00	76.2	.482	12.2	7.6	1.3	1.5	39	12	51	.84	21.4	0.059	1.5	14.3	SST	CG	N
0.600	15.24	71776	3.00	76.2	.474	12.0	12	2.1	1.8	45	21	92	.91	23.0	0.063	1.6	14.4	MW	CG	N
0.600	15.24	71776S	3.00	76.2	.474	12.0	10	1.8	1.4	36	14	62	.91	23.0	0.063	1.6	14.4	SST	CG	N
0.600	15.24	71790	3.00	76.2	.466	11.8	14	2.4	1.8	46	25	110	1.06	27.0	0.067	1.7	15.9	MW	CG	N
0.600	15.24	71790S	3.00	76.2	.466	11.8	12	2.0	1.4	37	17	75	1.06	27.0	0.067	1.7	15.9	SST	CG	N
0.600	15.24	71802	3.00	76.2	.456	11.6	18	3.2												



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.600	15.24	71834S	4.00	101.6	.430	10.9	26	4.6	1.2	31	32	142	1.69	42.9	0.085	2.2	19.9	SST	CG	N
0.600	15.24	71849	4.00	101.6	.416	10.6	43	7.6	1.3	34	57	256	1.85	47.0	0.092	2.3	20.1	MW	CG	N
0.600	15.24	71849S	4.00	101.6	.416	10.6	37	6.4	1.0	26	38	169	1.85	47.0	0.092	2.3	20.1	SST	CG	N
0.600	15.24	71864	4.00	101.6	.404	10.3	57	9.9	1.2	31	69	307	2.01	51.0	0.098	2.5	20.5	MW	CG	N
0.600	15.24	71864S	4.00	101.6	.404	10.3	48	8.4	.95	24	46	203	2.01	51.0	0.098	2.5	20.5	SST	CG	N
0.609	15.47	2574	.31	7.9	.569	14.5	.56	.10	.21	5.4	.12	.53	.10	2.5	0.020	0.5	4.00	MW	C	Z
0.609	15.47	EE-76	.38	9.5	.485	12.3	130	23	.11	2.7	14	62	.25	6.3	0.062	1.6	3.00	SPR	C	Z
0.609	15.47	AA-52	.41	10.3	.549	13.9	2.4	.42	.24	6.1	.58	2.6	.17	4.2	0.030	0.8	4.50	MW	C	N
0.609	15.47	J-53	.41	10.3	.465	11.8	221	39	.09	2.2	19	86	.22	5.5	0.072	1.8	3.00	SST	CG	N
0.609	15.47	NN-100	.44	11.1	.521	13.2	18	3.1	.24	6.1	4.2	19	.20	5.0	0.044	1.1	3.50	SST	C	N
0.609	15.47	Q-73	.44	11.1	.501	12.7	31	5.4	.22	5.6	6.9	31	.22	5.5	0.054	1.4	4.00	SST	CG	N
0.609	15.47	Q-37	.44	11.1	.459	11.7	130	23	.14	3.5	18	80	.30	7.6	0.075	1.9	4.00	SST	CG	N
0.609	15.47	I-100	.44	11.1	.409	10.4	1090	191	.05	1.2	52	229	.30	7.6	0.100	2.5	3.00	SPR	CG	Z
0.609	15.47	J-32	.47	11.9	.569	14.5	1.1	.20	.39	9.9	.44	1.9	.08	2.0	0.020	0.5	3.00	MW	C	N
0.609	15.47	K-41	.50	12.7	.539	13.7	5.7	1.0	.36	9.1	2.1	9.1	.14	3.6	0.035	0.9	4.00	SPR	CG	GI
0.609	15.47	WW-36	.50	12.7	.501	12.7	31	5.4	.23	5.8	7.1	32	.27	6.9	0.054	1.4	4.00	SST	C	N
0.609	15.47	UU-65	.50	12.7	.489	12.4	113	20	.11	2.9	13	57	.18	4.6	0.060	1.5	3.00	SPR	CG	Z
0.609	15.47	B15-26	.56	14.3	.509	12.9	26	4.5	.29	7.3	7.4	33	.20	5.1	0.050	1.3	4.00	SPR	CG	Z
0.609	15.47	10758	.56	14.3	.507	12.9	28	4.9	.28	7.2	7.9	35	.26	6.5	0.051	1.3	4.00	SPR	C	BO
0.609	15.47	B10-58	.63	15.9	.521	13.2	15	2.7	.34	8.6	5.1	23	.17	4.2	0.044	1.1	3.75	SST	CG	N
0.609	15.47	QQ-60	.63	15.9	.475	12.1	73	13	.24	6.2	18	78	.30	7.7	0.067	1.7	4.50	SPR	CG	Z
0.609	15.47	B17-120	.63	15.9	.385	9.8	801	140	.08	2.0	63	280	.45	11.4	0.112	2.8	4.00	SST	CG	N
0.609	15.47	Q-56	.66	16.7	.503	12.8	12	2.0	.29	7.2	3.3	15	.37	9.4	0.053	1.3	7.00	SST	CG	N
0.609	15.47	BB-98	.69	17.4	.545	13.8	1.6	.27	.46	12	.73	3.2	.22	5.7	0.032	0.8	7.00	SPR	CG	N
0.609	15.47	10618	.69	17.4	.537	13.6	6.4	1.1	.47	12	3.0	13	.18	4.6	0.036	0.9	4.00	SPR	C	Z
0.609	15.47	S-1108	.69	17.4	.489	12.4	24	4.3	.33	8.3	8.0	36	.36	9.1	0.060	1.5	6.00	SST	CG	N
0.609	15.47	10009	.69	17.5	.469	11.9	73	13	.26	6.6	19	85	.35	8.9	0.070	1.8	5.00	SPR	CG	Z
0.609	15.47	10953	.72	18.2	.523	13.3	6.8	1.2	.42	11	2.8	13	.30	7.6	0.043	1.1	6.00	SPR	C	N
0.609	15.47	2780	.75	19.1	.539	13.7	3.3	.57	.52	13	1.7	7.6	.23	5.8	0.035	0.9	5.50	HD	C	Z
0.609	15.47	N-30	.75	19.1	.525	13.3	6.2	1.1	.52	13	3.2	14	.23	5.9	0.042	1.1	5.50	SST	CG	N
0.609	15.47	PP-43	.75	19.1	.449	11.4	133	23	.21	5.4	28	125	.40	10.2	0.080	2.0	5.00	SPR	CG	Z
0.609	15.47	12258	.75	19.1	.445	11.3	127	22	.24	6.1	30	134	.45	11.5	0.082	2.1	5.50	SPR	CG	Z
0.609	15.47	2682	.75	19.1	.427	10.8	236	41	.23	5.9	55	244	.46	11.6	0.091	2.3	5.00	MW	CG	Z
0.609	15.47	S-1690	.80	20.3	.469	11.9	64	11	.28	7.1	18	79	.35	8.9	0.070	1.8	5.00	SST	CG	N
0.609	15.47	1769	.81	20.6	.549	13.9	2.4	.42	.65	16	1.6	6.9	.17	4.2	0.030	0.8	4.50	HD	C	Z
0.609	15.47	4146	.81	20.6	.439	11.2	130	23	.26	6.5	34	149	.51	13.0	0.085	2.2	6.00	SPR	CG	Z
0.609	15.47	S-1700	.82	20.9	.465	11.8	72	13	.27	6.8	19	86	.43	11.0	0.072	1.8	5.00	SST	C	N
0.609	15.47	12778	.88	22.2	.509	12.9	18	3.1	.39	9.9	7.0	31	.28	7.0	0.050	1.3	4.50	SST	C	N
0.609	15.47	J-63	.88	22.2	.499	12.7	26	4.5	.38	9.7	9.9	44	.28	7.0	0.055	1.4	5.00	SPR	C	Z
0.609	15.47	11032	.88	22.2	.463	11.8	64	11	.31	8.0	20	90	.41	10.5	0.073	1.9	5.67	SST	CG	N
0.609	15.47	S-266	.91	23.0	.499	12.7	23	4.0	.41	10	9.3	41	.33	8.4	0.055	1.4	5.00	SST	C	N
0.609	15.47	2785	.91	23.0	.497	12.6	28	4.9	.37	9.5	10	46	.34	8.5	0.056	1.4	5.00	SPR	C	Z
0.609	15.47	N-67	.94	23.8	.469	11.9	55	9.6	.35	8.8	19	85	.49	12.4	0.070	1.8	6.00	SPR	C	Z
0.609	15.47	2779	.94	23.8	.427	10.8	164	29	.34	8.5	55	244	.58	14.6	0.091	2.3	6.33	MW	CG	Z
0.609	15.47	11449	1.00	25.4	.563	14.3	.24	.04	.74	19	.17	.77	.26	6.7	0.023	0.6	10.5	MW	C	N
0.609	15.47	L-37	1.00	25.4	.539	13.7	3.8	.67	.73	18	2.8	12	.21	5.3	0.035	0.9	5.00	SPR	C	Z
0.609	15.47	3889	1.00	25.4	.519	13.2	6.6	1.2	.64	16	4.2	19	.36	9.1	0.045	1.1	7.00	SPR	C	Z
0.609	15.47	S-926	1.00	25.4	.519	13.2	7.1	1.3	.73	19	5.2	23	.27	6.9	0.045	1.1	6.00	SST	CG	N
0.609	15.47	Q-33	1.00	25.4	.475	12.1	29	5.0	.50	13	14	64	.50	12.8	0.067	1.7	7.50	SST	CG	N
0.609	15.47	B15-64	1.00	25.4	.467	11.9	59	10	.31	7.9	19	83	.39	9.9	0.071	1.8	5.50	SST	CG	N
0.609	15.47	G-48	1.00	25.4	.465	11.8	55	9.7	.37	9.5	21	92	.47	11.9	0.072	1.8	6.50	HD	CG	N
0.609	15.47	11245	1.03	26.2	.485	12.3	37	6.5	.53	13	19	87	.34	8.7	0.062	1.6	5.50	MW	CG	N
0.609	15.47	S-3209	1.06	27.0	.531	13.5	5.3	.93	.67	17	3.6	16	.23	5.9	0.039	1.0	5.00	SST	C	N
0.609	15.47	12594	1.08	27.4	.301	7.6	2020	354	.08	2.0	158	705	.96	24.5	0.154	3.9	6.25	SPR	CG	GI
0.609	15.47	10611	1.09	27.8	.535	13.6	4.1	.72	.79	20	3.3	15	.24	6.1	0.037	0.9	5.50	SPR	C	Z
0.609	15.47	S-1564	1.11	28.2	.449	11.4	53	9.3	.43	11	23	102	.68	17.3	0.080	2.0	8.50	SST	CG	N
0.609	15.47	S-259	1.13	28.6	.545	13.8	1.4	.24	.87	22	1.2	5.3	.26	6.5	0.032	0.8	7.00	SST	C	N
0.609	15.47	3107	1.13	28.6	.527	13.4	5><													




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.609	15.47	S-1192	1.44	36.5	.425	10.8	118	21	.32	8.1	38	167	.69	17.5	0.092	2.3	7.50	SST	CG	N
0.609	15.47	LL-92	1.50	38.1	.527	13.4	3.9	.68	1.1	29	4.4	20	.36	9.1	0.041	1.0	7.75	SPR	C	GI
0.609	15.47	S-1406	1.50	38.1	.521	13.2	3.2	.57	1.1	27	3.4	15	.44	11.2	0.044	1.1	10.0	SST	CG	N
0.609	15.47	S-1311	1.50	38.1	.501	12.7	11	2.0	.78	20	8.8	39	.41	10.3	0.054	1.4	7.50	SST	CG	N
0.609	15.47	S-938	1.50	38.1	.501	12.7	9.6	1.7	.92	23	8.8	39	.46	11.7	0.054	1.4	8.50	SST	CG	N
0.609	15.47	11310	1.50	38.1	.489	12.4	13	2.3	.87	22	12	51	.63	16.0	0.060	1.5	10.5	SPR	CG	Z
0.609	15.47	Q-60	1.50	38.1	.451	11.5	32	5.6	.51	13	16	72	.99	25.1	0.079	2.0	12.5	SST	CG	N
0.609	15.47	S-485	1.53	38.9	.519	13.2	5.2	.91	1.1	27	5.5	24	.34	8.6	0.045	1.1	7.50	SST	CG	N
0.609	15.47	11653	1.53	38.9	.449	11.4	33	5.8	.41	10	14	61	1.12	28.4	0.080	2.0	14.0	SPR	CG	Z
0.609	15.47	YY-30	1.56	39.7	.503	12.8	11	1.9	.80	20	8.8	39	.48	12.1	0.053	1.3	8.00	SPR	C	Z
0.609	15.47	A15-67	1.56	39.7	.403	10.2	147	26	.38	9.7	56	250	1.08	27.5	0.103	2.6	10.5	SPR	CG	Z
0.609	15.47	S-1143	1.63	41.3	.501	12.7	8.3	1.5	1.1	27	8.8	39	.51	13.0	0.054	1.4	9.50	SST	CG	N
0.609	15.47	11511	1.63	41.3	.467	11.9	29	5.1	.68	17	20	88	.78	19.8	0.071	1.8	10.0	SPR	CG	Z
0.609	15.47	10189	1.63	41.3	.427	10.8	71	12	.53	14	38	168	1.09	27.7	0.091	2.3	12.0	SPR	CG	GI
0.609	15.47	10846	1.63	41.3	.369	9.4	323	57	.24	6.0	77	341	1.08	27.4	0.120	3.0	9.00	SST	CG	N
0.609	15.47	S-1213	1.63	41.3	.297	7.6	1293	226	.12	3.1	156	693	1.41	35.7	0.156	3.9	9.00	SST	CG	N
0.609	15.47	B10-15	1.66	42.1	.499	12.7	9.7	1.7	1.0	26	9.9	44	.61	15.4	0.055	1.4	10.0	SPR	C	Z
0.609	15.47	2537	1.69	42.8	.513	13.0	3.9	.69	1.1	27	4.2	19	.62	15.8	0.048	1.2	13.0	SPR	CG	GI
0.609	15.47	S-885	1.69	42.8	.365	9.3	355	62	.23	5.7	80	357	1.07	27.1	0.122	3.1	8.75	SST	CG	N
0.609	15.47	11581	1.75	44.5	.489	12.4	14	2.5	.91	23	13	57	.66	16.8	0.060	1.5	10.0	SPR	CG	N
0.609	15.47	S-494	1.75	44.5	.465	11.8	24	4.2	.80	20	19	86	.79	20.1	0.072	1.8	11.0	SST	CG	N
0.609	15.47	1517	1.75	44.5	.413	10.5	114	20	.43	11	49	216	1.05	26.8	0.098	2.5	10.8	SPR	CG	Z
0.609	15.47	JJ-78	1.81	46.0	.545	13.8	.98	.17	1.5	37	1.4	6.4	.35	8.9	0.032	0.8	10.0	SPR	C	Z
0.609	15.47	11886	1.84	46.8	.445	11.3	49	8.6	.61	16	30	134	.90	22.9	0.082	2.1	11.0	SPR	CG	N
0.609	15.47	11939	1.84	46.8	.409	10.4	91	16	.44	11	40	179	1.40	35.6	0.100	2.5	14.0	SPR	CG	Z
0.609	15.47	12510	1.84	46.8	.483	12.3	16	2.8	1.1	28	18	78	.74	18.8	0.063	1.6	10.8	MW	C	N
0.609	15.47	12256	1.88	47.6	.419	10.6	108	19	.41	10	44	198	.95	24.1	0.095	2.4	10.0	SPR	CG	Z
0.609	15.47	S-24	2.00	50.8	.519	13.2	3.6	.63	1.5	38	5.4	24	.50	12.6	0.045	1.1	10.0	SST	C	N
0.609	15.47	S-277	2.00	50.8	.439	11.2	57	9.9	.55	14	31	140	.85	21.6	0.085	2.2	10.0	SST	CG	N
0.609	15.47	11792	2.00	50.8	.421	10.7	82	14	.53	13	43	192	1.13	28.7	0.094	2.4	12.0	SPR	CG	Z
0.609	15.47	10564	2.03	51.6	.505	12.8	6.2	1.1	1.3	34	8.4	37	.61	15.5	0.052	1.3	11.8	SPR	CG	Z
0.609	15.47	10961	2.13	54.0	.561	14.2	.50	.09	1.9	49	.97	4.3	.19	4.7	0.024	0.6	6.75	MW	C	Z
0.609	15.47	11689	2.25	57.2	.501	12.7	7.9	1.4	1.2	30	9.3	42	.59	15.1	0.054	1.4	11.0	SPR	CG	Z
0.609	15.47	11487	2.25	57.2	.399	10.1	105	18	.57	14	59	264	1.68	42.7	0.105	2.7	15.0	SPR	CG	Z
0.609	15.47	10501	2.28	57.9	.463	11.8	27	4.6	.81	21	22	96	.88	22.3	0.073	1.9	12.0	SPR	CG	Z
0.609	15.47	B14-45	2.34	59.5	.409	10.4	91	16	.57	14	52	229	1.40	35.6	0.100	2.5	14.0	SPR	CG	Z
0.609	15.47	S-74	2.38	60.3	.339	8.6	487	85	.21	5.3	102	454	1.35	34.3	0.135	3.4	10.0	SST	CG	N
0.609	15.47	S-3255	2.41	61.1	.519	13.2	3.9	.68	1.4	36	5.5	24	.43	10.9	0.045	1.1	9.50	SST	CG	N
0.609	15.47	10711	2.41	61.1	.373	9.5	235	41	.34	8.6	80	356	1.42	36.0	0.118	3.0	12.0	SPR	CG	Z
0.609	15.47	VV-56	2.50	63.5	.525	13.3	1.9	.34	1.9	49	3.7	16	.59	14.9	0.042	1.1	13.0	SST	C	N
0.609	15.47	11622	2.50	63.5	.519	13.2	3.3	.58	1.8	45	5.8	26	.54	13.7	0.045	1.1	12.0	SPR	CG	GI
0.609	15.47	B2-63	2.50	63.5	.485	12.3	12	2.1	1.6	41	19	86	.87	22.0	0.062	1.6	13.0	MW	C	Z
0.609	15.47	11249	2.50	63.5	.413	10.5	71	12	.69	17	49	216	1.57	39.8	0.098	2.5	16.0	SPR	CG	Z
0.609	15.47	11657	2.53	64.3	.399	10.1	171	30	.35	8.8	59	264	1.05	26.7	0.105	2.7	10.0	SPR	CG	Z
0.609	15.47	11958	2.59	65.9	.531	13.5	1.0	.17	1.8	45	1.8	7.9	.82	20.8	0.039	1.0	20.0	SPR	C	Z
0.609	15.47	11790	2.59	65.9	.461	11.7	28	4.9	.80	20	22	100	.89	22.6	0.074	1.9	12.0	SPR	CG	Z
0.609	15.47	VW-50	2.75	69.9	.529	13.4	2.2	.38	1.8	45	3.9	17	.44	11.2	0.040	1.0	10.0	SST	C	N
0.609	15.47	4105	2.75	69.9	.527	13.4	1.8	.32	2.1	54	3.9	18	.62	15.6	0.041	1.0	14.0	SPR	C	Z
0.609	15.47	2867	2.75	69.9	.471	12.0	16	2.8	1.7	42	27	119	1.03	26.1	0.069	1.8	15.0	MW	CG	Z
0.609	15.47	11840	2.78	70.6	.467	11.9	21	3.7	.93	24	20	88	.92	23.4	0.071	1.8	13.0	SPR	CG	Z
0.609	15.47	12142	2.88	73.0	.525	13.3	1.1	.19	1.8	45	1.9	8.5	1.09	27.7	0.042	1.1	25.0	SPR	C	Z
0.609	15.47	3660	3.25	82.6	.525	13.3	2.5	.44	1.9	48	4.8	21	.49	12.5	0.042	1.1	11.8	SPR	CG	Z
0.609	15.47	10769	3.25	82.6	.485	12.3	11	1.9	1.3	32	14	62	.85	21.7	0.062	1.6	13.8	SPR	CG	GI
0.609	15.47	11556	3.38	85.7	.559	14.2	.28	.05	3.1	77	.86	3.8	.33	8.3	0.025	0.6	12.0	MW	C	Z
0.609	15.47	2710	3.50	88.9	.513	13.0	2.7	.47	2.6	66	7.0	31	.91	23.2	0.048	1.2	18.0	HD	C	Z
0.609	15.47	S-215	3.50	88.9	.485	12.3	7.1	1.2	1.9	48	13	59	1.12	28.3	0.062	1.6	18.0	SST	CG	N
0.609	15.47	10863	3.50	88.9	.427	10.8	43	7.5	.91	23	39	175	1.68	42.8	0.091	2.3	18.5	SPR	CG	N
0.609	15.47	3199	3.53	89.7	.513															



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.625	15.88	B9-39	.66	16.7	.521	13.2	19	3.3	.40	10	7.4	33	.26	6.6	0.052	1.3	5.00	SPR	CG	N
0.625	15.88	XX-56	.69	17.4	.545	13.8	8.0	1.4	.47	12	3.8	17	.20	5.1	0.040	1.0	4.00	SST	C	N
0.625	15.88	A9-66	.72	18.2	.561	14.2	2.3	.41	.57	14	1.3	5.9	.15	3.8	0.032	0.8	4.75	SST	CG	N
0.625	15.88	522	.75	19.1	.543	13.8	10	1.8	.42	11	4.3	19	.21	5.2	0.041	1.0	4.00	HD	C	Z
0.625	15.88	918	.75	19.1	.543	13.8	6.8	1.2	.50	13	3.4	15	.25	6.2	0.041	1.0	5.00	HD	C	Z
0.625	15.88	CC-24	.75	19.1	.525	13.3	16	2.8	.46	12	7.3	32	.25	6.4	0.050	1.3	5.00	SPR	CG	Z
0.625	15.88	S-766	.75	19.1	.515	13.1	27	4.8	.33	8.4	9.0	40	.29	7.3	0.055	1.4	4.25	SST	C	N
0.625	15.88	S-286	.75	19.1	.481	12.2	50	8.7	.32	8.1	16	70	.43	11.0	0.072	1.8	6.00	SST	CG	N
0.625	15.88	10279	.75	19.1	.465	11.8	182	32	.15	3.8	27	122	.32	8.1	0.080	2.0	4.00	SPR	CG	Z
0.625	15.88	4205	.75	19.1	.415	10.5	414	73	.14	3.6	58	258	.53	13.3	0.105	2.7	5.00	SPR	CG	Z
0.625	15.88	S-58	.78	19.8	.501	12.7	69	12	.19	4.7	13	57	.22	5.5	0.062	1.6	3.50	SST	CG	N
0.625	15.88	K-59	.78	19.8	.445	11.3	154	27	.24	6.1	37	165	.54	13.7	0.090	2.3	6.00	SPR	CG	N
0.625	15.88	A11-43	.81	20.6	.519	13.2	23	4.0	.35	8.9	8.1	36	.23	5.8	0.053	1.3	4.33	SST	CG	N
0.625	15.88	S-826	.81	20.6	.425	10.8	247	43	.19	4.8	47	208	.55	14.0	0.100	2.5	5.50	SST	CG	N
0.625	15.88	10888	.84	21.4	.589	15.0	.17	.03	.73	18	.12	.55	.12	3.0	0.018	0.5	5.50	SST	C	N
0.625	15.88	S-68	.88	22.2	.549	13.9	4.7	.82	.69	17	3.2	14	.18	4.6	0.038	1.0	4.75	SST	CG	N
0.625	15.88	2831	.88	22.2	.531	13.5	7.3	1.3	.50	13	3.6	16	.38	9.6	0.047	1.2	7.00	HD	C	Z
0.625	15.88	B12-58	.88	22.2	.515	13.1	14	2.5	.49	12	7.0	31	.39	9.8	0.055	1.4	7.00	SPR	CG	Z
0.625	15.88	3911	.88	22.2	.501	12.7	30	5.2	.46	12	14	61	.37	9.4	0.062	1.6	6.00	HD	CG	Z
0.625	15.88	3192	.88	22.2	.439	11.2	238	42	.17	4.4	41	182	.47	11.8	0.093	2.4	5.00	SPR	CG	Z
0.625	15.88	10982	.88	22.2	.431	10.9	219	38	.20	5.0	43	190	.53	13.6	0.097	2.5	5.50	SST	CG	N
0.625	15.88	A9-69	.91	23.0	.543	13.8	7.4	1.3	.58	15	4.3	19	.19	4.9	0.041	1.0	4.75	SPR	CG	Z
0.625	15.88	W-30	.94	23.8	.551	14.0	1.5	.26	.49	13	.73	3.2	.44	11.3	0.037	0.9	11.0	SPR	C	Z
0.625	15.88	AA-75	.94	23.8	.505	12.8	28	4.8	.45	11	12	55	.35	8.8	0.060	1.5	5.75	SPR	CG	N
0.625	15.88	3129	.97	24.6	.563	14.3	2.1	.37	.78	20	1.7	7.3	.19	4.7	0.031	0.8	5.00	MW	C	Z
0.625	15.88	3031	1.00	25.4	.539	13.7	5.5	.97	.68	17	3.8	17	.32	8.2	0.043	1.1	6.50	SPR	C	Z
0.625	15.88	2799	1.00	25.4	.533	13.5	13	2.3	.46	12	6.1	27	.21	5.3	0.046	1.2	4.50	SPR	CG	GI
0.625	15.88	B11-59	1.00	25.4	.529	13.4	11	2.0	.61	15	6.9	31	.26	6.7	0.048	1.2	5.50	SPR	CG	N
0.625	15.88	11456	1.00	25.4	.521	13.2	14	2.4	.58	15	8.1	36	.36	9.2	0.052	1.3	6.00	SPR	C	Z
0.625	15.88	N-53	1.00	25.4	.517	13.1	13	2.3	.62	16	8.2	36	.38	9.6	0.054	1.4	7.00	SPR	CG	GI
0.625	15.88	S-767	1.00	25.4	.515	13.1	19	3.3	.48	12	9.0	40	.34	8.7	0.055	1.4	5.25	SST	C	N
0.625	15.88	12121	1.00	25.4	.509	12.9	11	2.0	.36	9.2	4.0	18	.64	16.2	0.058	1.5	10.0	SPR	C	Z
0.625	15.88	S-770	1.00	25.4	.499	12.7	32	5.6	.43	11	14	60	.41	10.4	0.063	1.6	5.50	SST	C	N
0.625	15.88	EE-40	1.00	25.4	.485	12.3	50	8.8	.37	9.4	19	83	.42	10.7	0.070	1.8	6.00	SPR	CG	N
0.625	15.88	S-367	1.00	25.4	.481	12.2	50	8.7	.38	9.7	19	84	.43	11.0	0.072	1.8	6.00	SST	CG	N
0.625	15.88	944	1.00	25.4	.465	11.8	121	21	.23	5.8	27	122	.48	12.2	0.080	2.0	5.00	HD	C	Z
0.625	15.88	2745	1.00	25.4	.455	11.6	159	28	.29	7.3	46	204	.43	10.8	0.085	2.2	5.00	MW	CG	Z
0.625	15.88	10354	1.03	26.2	.471	12.0	51	9.0	.42	11	21	94	.62	15.6	0.077	2.0	8.00	SPR	CG	Z
0.625	15.88	BB-88	1.06	27.0	.547	13.9	3.3	.58	.79	20	2.6	12	.27	6.9	0.039	1.0	7.00	SPR	CG	Z
0.625	15.88	B15-24	1.06	27.0	.535	13.6	10	1.8	.56	14	5.7	25	.23	5.7	0.045	1.1	5.00	SPR	CG	N
0.625	15.88	S-1451	1.06	27.0	.509	12.9	14	2.5	.63	16	8.8	39	.44	11.0	0.058	1.5	7.50	SST	CG	N
0.625	15.88	L-64	1.06	27.0	.491	12.5	28	4.9	.53	13	15	65	.54	13.6	0.067	1.7	8.00	SPR	CG	N
0.625	15.88	12289	1.06	27.0	.435	11.0	157	28	.28	7.0	43	193	.67	16.9	0.095	2.4	7.00	SPR	CG	GI
0.625	15.88	3856	1.06	27.0	.371	9.4	757	133	.13	3.2	96	429	.76	19.4	0.127	3.2	6.00	SPR	CG	Z
0.625	15.88	12469	1.09	27.8	.495	12.6	27	4.7	.59	15	16	70	.49	12.4	0.065	1.7	7.50	SPR	CG	Z
0.625	15.88	10747	1.09	27.8	.415	10.5	220	39	.24	6.2	54	239	.74	18.7	0.105	2.7	7.00	SST	CG	N
0.625	15.88	4317	1.13	28.6	.575	14.6	.58	.10	.94	24	.54	2.4	.19	4.8	0.025	0.6	6.50	MW	C	Z
0.625	15.88	S-1588	1.13	28.6	.507	12.9	14	2.5	.65	17	9.3	41	.47	12.0	0.059	1.5	8.00	SST	CG	N
0.625	15.88	S-890	1.13	28.6	.491	12.5	26	4.6	.61	16	16	72	.50	12.8	0.067	1.7	7.50	SST	CG	N
0.625	15.88	S-1423	1.13	28.6	.481	12.2	33	5.8	.55	14	18	81	.58	14.6	0.072	1.8	8.00	SST	CG	N
0.625	15.88	12190	1.13	28.6	.425	10.8	136	24	.28	7.0	37	166	.85	21.6	0.100	2.5	8.50	SPR	CG	Z
0.625	15.88	L-50	1.13	28.6	.415	10.5	355	62	.16	4.2	58	258	.58	14.7	0.105	2.7	5.50	SPR	CG	Z
0.625	15.88	2972	1.16	29.4	.551	14.0	1.4	.24	.73	19	1.0	4.5	.43	10.8	0.037	0.9	11.5	SPR	CG	Z
0.625	15.88	12137	1.16	29.4	.525	13.3	12	2.1	.61	16	7.3	32	.30	7.6	0.050	1.3	6.00	SPR	CG	Z
0.625	15.88	3980	1.16	29.4	.329	8.4	1338	234	.11	2.7	143	637	1.00	25.4	0.148	3.8	6.75	SPR	CG	N
0.625	15.88	S-117	1.19	30.2	.561	14.2	1.3	.22	.93	24	1.2	5.3	.26	6.5	0.032	0.8	7.00	SST	C	N
0.625	15.88	10750	1.19	30.2	.537	13.6	5.5	.96	.88	22	4.8	22	.31	7.8	0.044	1.1	7.00	SPR	CG	Z
0.625	15.88	B15-58	1.19	30.2	.															



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./in.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.625	15.88	3879	1.44	36.5	.551	14.0	1.5	.26	.99	25	1.5	6.5	.44	11.3	0.037	0.9	11.0	SPR	C	Z
0.625	15.88	A10-59	1.44	36.5	.481	12.2	29	5.0	.71	18	20	90	.72	18.3	0.072	1.8	10.0	SPR	CG	Z
0.625	15.88	S-1225	1.44	36.5	.455	11.6	64	11	.48	12	31	137	.72	18.4	0.085	2.2	8.50	SST	CG	N
0.625	15.88	10452	1.47	37.3	.477	12.1	32	5.6	.68	17	22	97	.74	18.8	0.074	1.9	10.0	SPR	CG	Z
0.625	15.88	11473	1.50	38.1	.555	14.1	1.4	.25	1.1	29	1.7	7.4	.36	9.1	0.035	0.9	9.25	MW	C	Z
0.625	15.88	523	1.50	38.1	.543	13.8	3.4	.60	1.1	29	3.8	17	.37	9.4	0.041	1.0	8.00	HD	C	Z
0.625	15.88	S-1186	1.50	38.1	.531	13.5	5.3	.92	1.1	27	5.7	25	.42	10.7	0.047	1.2	8.00	SST	C	N
0.625	15.88	4213	1.50	38.1	.529	13.4	6.9	1.2	1.0	25	6.9	31	.42	10.7	0.048	1.2	7.75	SPR	C	Z
0.625	15.88	S-769	1.50	38.1	.515	13.1	12	2.1	.77	20	9.0	40	.45	11.5	0.055	1.4	7.25	SST	C	N
0.625	15.88	S-772	1.50	38.1	.499	12.7	19	3.4	.70	18	14	60	.55	14.0	0.063	1.6	7.75	SST	C	N
0.625	15.88	S-773	1.50	38.1	.481	12.2	32	5.6	.59	15	19	84	.67	16.9	0.072	1.8	8.25	SST	C	N
0.625	15.88	XX-58	1.50	38.1	.481	12.2	28	5.0	.67	17	19	84	.65	16.5	0.072	1.8	9.00	SST	CG	N
0.625	15.88	11304	1.50	38.1	.451	11.5	82	14	.40	10	33	146	.76	19.3	0.087	2.2	7.75	SST	C	N
0.625	15.88	11445	1.50	38.1	.435	11.0	157	28	.39	9.8	61	270	.67	16.9	0.095	2.4	7.00	MW	CG	Z
0.625	15.88	3917	1.63	41.3	.529	13.4	3.6	.63	.95	24	3.4	15	.67	17.1	0.048	1.2	13.0	HD	C	Z
0.625	15.88	3252	1.63	41.3	.465	11.8	40	7.1	.68	17	27	122	.88	22.4	0.080	2.0	11.0	HD	CG	Z
0.625	15.88	11688	1.69	42.8	.531	13.5	3.5	.61	1.1	28	3.8	17	.59	14.9	0.047	1.2	12.5	SPR	CG	Z
0.625	15.88	4128	1.69	42.8	.445	11.3	103	18	.36	9.2	37	165	.81	20.6	0.090	2.3	8.00	SPR	C	Z
0.625	15.88	3887	1.69	42.8	.355	9.0	541	95	.21	5.2	111	494	1.28	32.6	0.135	3.4	9.50	SPR	CG	Z
0.625	15.88	4125	1.75	44.5	.481	12.2	33	5.7	.62	16	20	90	.72	18.3	0.072	1.8	9.00	SPR	C	Z
0.625	15.88	S-774	1.75	44.5	.481	12.2	26	4.6	.71	18	19	84	.76	19.2	0.072	1.8	9.50	SST	C	N
0.625	15.88	882	1.75	44.5	.443	11.3	72	13	.53	14	38	171	1.09	27.7	0.091	2.3	11.0	HD	C	Z
0.625	15.88	S-3259	1.78	45.2	.565	14.4	1.2	.21	1.4	34	1.7	7.4	.18	4.6	0.030	0.8	6.00	SST	CG	N
0.625	15.88	B18-134	1.78	45.2	.329	8.4	794	139	.15	3.9	122	541	1.63	41.4	0.148	3.8	10.0	SPR	CG	N
0.625	15.88	S-1568	1.81	46.0	.497	12.6	15	2.7	.93	24	14	63	.64	16.3	0.064	1.6	10.0	SST	CG	N
0.625	15.88	11124	1.81	46.0	.443	11.3	66	12	.58	15	38	171	1.16	29.5	0.091	2.3	11.8	HD	C	Z
0.625	15.88	3209	1.84	46.8	.443	11.3	65	11	.59	15	38	171	1.09	27.7	0.091	2.3	12.0	SPR	CG	Z
0.625	15.88	4295	1.88	47.6	.531	13.5	8.1	1.4	.80	20	6.5	29	.31	7.8	0.047	1.2	6.50	SPR	CG	Z
0.625	15.88	B32-32	1.91	48.4	.483	12.3	19	3.3	.95	24	18	81	.85	21.6	0.071	1.8	12.0	SST	CG	N
0.625	15.88	11852	2.00	50.8	.567	14.4	.87	.15	1.8	45	1.6	6.9	.22	5.5	0.029	0.7	7.50	MW	CG	N
0.625	15.88	S-775	2.00	50.8	.481	12.2	23	4.0	.83	21	19	84	.85	21.5	0.072	1.8	10.8	SST	C	N
0.625	15.88	B8-28	2.00	50.8	.475	12.1	29	5.0	.79	20	23	101	.86	21.9	0.075	1.9	11.5	SPR	CG	N
0.625	15.88	12272	2.09	53.2	.501	12.7	13	2.3	1.0	26	14	61	.68	17.3	0.062	1.6	11.0	SPR	CG	Z
0.625	15.88	11767	2.09	53.2	.465	11.8	33	5.8	.83	21	27	122	1.04	26.4	0.080	2.0	13.0	SPR	CG	Z
0.625	15.88	11295	2.19	55.6	.459	11.7	37	6.5	.82	21	31	136	1.12	28.5	0.083	2.1	13.5	SPR	CG	Z
0.625	15.88	B18-153	2.22	56.4	.425	10.8	81	14	.62	16	50	224	1.43	36.2	0.100	2.5	14.3	SPR	CG	Z
0.625	15.88	S-1470	2.25	57.2	.559	14.2	1.4	.25	1.5	39	2.2	9.8	.23	5.9	0.033	0.8	7.00	SST	CG	N
0.625	15.88	4260	2.25	57.2	.501	12.7	13	2.3	1.0	26	14	61	.74	18.9	0.062	1.6	11.0	SPR	C	Z
0.625	15.88	916	2.25	57.2	.481	12.2	20	3.5	1.0	26	20	90	1.04	26.5	0.072	1.8	13.5	HD	C	Z
0.625	15.88	2672	2.25	57.2	.415	10.5	113	20	.51	13	58	258	1.37	34.7	0.105	2.7	13.0	SPR	CG	Z
0.625	15.88	11438	2.25	57.2	.401	10.2	134	23	.50	13	68	300	1.62	41.2	0.112	2.8	14.5	SPR	CG	Z
0.625	15.88	S-809	2.31	58.7	.355	9.0	483	85	.21	5.3	100	445	1.37	34.8	0.135	3.4	10.0	SST	CG	N
0.625	15.88	47	2.38	60.3	.415	10.5	104	18	.56	14	58	258	1.47	37.3	0.105	2.7	14.0	HD	CG	Z
0.625	15.88	Q-42	2.44	61.9	.483	12.3	16	2.8	1.2	31	19	86	1.17	29.8	0.071	1.8	15.5	SPR	C	N
0.625	15.88	2512	2.44	61.9	.415	10.5	124	22	.65	17	81	361	1.37	34.7	0.105	2.7	12.0	MW	C	Z
0.625	15.88	2838	2.44	61.9	.385	9.8	209	37	.58	15	120	535	1.60	40.5	0.120	3.1	13.0	MW	CG	Z
0.625	15.88	S-776	2.50	63.5	.481	12.2	18	3.1	1.1	27	19	84	1.03	26.1	0.072	1.8	13.3	SST	C	N
0.625	15.88	1787	2.50	63.5	.465	11.8	29	5.1	.94	24	27	122	1.24	31.5	0.080	2.0	14.5	SPR	C	Z
0.625	15.88	23	2.50	63.5	.465	11.8	32	5.7	.85	22	27	122	1.14	29.0	0.080	2.0	13.3	HD	C	Z
0.625	15.88	12279	2.50	63.5	.453	11.5	36	6.3	.95	24	34	151	1.38	35.0	0.086	2.2	16.0	SPR	CG	Z
0.625	15.88	S-1371	2.50	63.5	.329	8.4	460	81	.28	7.1	129	574	2.07	52.6	0.148	3.8	14.0	SST	CG	N
0.625	15.88	S-871	2.53	64.3	.463	11.8	32	5.6	.84	21	27	119	1.01	25.7	0.081	2.1	12.5	SST	CG	N
0.625	15.88	1791	2.53	64.3	.329	8.4	508	89	.39	9.8	196	871	2.15	54.5	0.148	3.8	14.5	MW	CG	Z
0.625	15.88	11654	2.56	65.1	.495	12.6	12	2.1	1.3	33	16	70	.98	24.8	0.065	1.7	14.0	SPR	C	Z
0.625	15.88	S-91	2.63	66.7	.375	9.5	212	37	.40	10	84	374	1.69	42.9	0.125	3.2	13.5	SST	CG	N
0.625	15.88	21	2.75	69.9	.517	13.1	5.8	1.0	1.6	40	9.1	41	.77	19.6	0.054	1.4	13.3	HD	C	Z
0.625	15.88	1607	2.75	69.9	.515	13.1	4.4	.78	1.7	43	7.6	34	1.05	26.5	0.055	1.4	18.0	SPR	C	Z
0.625	15.88	3246	2.75	69.9																



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.625	15.88	1899	4.81	122.2	.449	11.4	24	4.3	2.1	53	51	225	2.18	55.3	0.088	2.2	24.8	MW	CG	Z
0.625	15.88	12419	4.84	123.0	.443	11.3	27	4.7	1.4	36	38	171	2.37	60.1	0.091	2.3	26.0	SPR	CG	N
0.625	15.88	12441	4.94	125.4	.441	11.2	27	4.7	1.5	38	40	176	2.62	66.6	0.092	2.3	27.5	SPR	C	N
0.625	15.88	874	5.00	127.0	.443	11.3	24	4.2	1.6	41	38	171	2.64	67.0	0.091	2.3	29.0	HD	CG	Z
0.625	15.88	3803	5.00	127.0	.441	11.2	25	4.4	1.6	40	40	176	2.76	70.1	0.092	2.3	29.0	SPR	CG	Z
0.625	15.88	870	5.00	127.0	.415	10.5	41	7.1	1.4	36	58	258	3.43	87.1	0.105	2.7	32.7	HD	CG	Z
0.625	15.88	1657	6.00	152.4	.517	13.1	2.8	.49	3.2	82	9.1	41	1.42	36.0	0.054	1.4	25.3	SPR	C	Z
0.625	15.88	3334	6.00	152.4	.481	12.2	5.8	1.0	3.0	77	17	77	2.99	75.9	0.072	1.8	41.5	HD	CG	GI
0.625	15.88	1944	7.00	177.8	.455	11.6	15	2.6	2.2	56	33	146	2.98	75.6	0.085	2.2	34.0	SPR	C	Z
0.625	15.88	888	9.00	228.6	.465	11.8	8.4	1.5	3.3	83	27	122	3.72	94.5	0.080	2.0	45.5	HD	C	Z
0.625	15.88	10542	9.50	241.3	.477	12.1	6.1	1.1	3.6	91	22	97	3.33	84.6	0.074	1.9	44.0	SPR	C	Z
0.625	15.88	10150	9.75	247.7	.443	11.3	15	2.5	2.6	67	38	171	4.32	109.8	0.091	2.3	46.5	SPR	C	Z
0.625	15.88	4143	11.9	301.6	.481	12.2	4.0	.70	5.0	128	20	90	4.32	109.7	0.072	1.8	59.0	HD	C	Z
0.625	15.88	881	12.0	304.8	.501	12.7	2.1	.36	6.7	169	14	61	3.78	96.1	0.062	1.6	60.0	HD	C	Z
0.625	15.88	878	12.0	304.8	.481	12.2	3.5	.62	5.7	145	20	90	4.86	123.4	0.072	1.8	66.0	HD	C	Z
0.625	15.88	876	12.0	304.8	.465	11.8	6.2	1.1	4.4	112	27	122	4.92	125.0	0.080	2.0	60.0	HD	C	Z
0.625	15.88	S-3045	15.0	381.0	.491	12.5	1.9	.34	8.4	214	16	72	5.19	131.9	0.067	1.7	77.0	SST	CG	N
0.640	16.26	S-105	.34	8.7	.582	14.8	3.1	.54	.22	5.6	.68	3.0	.12	3.1	0.029	0.7	3.25	SST	C	N
0.640	16.26	B10-13	.38	9.5	.508	12.9	57	10	.09	2.4	5.4	24	.28	7.1	0.066	1.7	4.25	SST	CG	N
0.640	16.26	O-70	.41	10.3	.516	13.1	110	19	.12	3.1	13	60	.19	4.7	0.062	1.6	3.00	SPR	CG	Z
0.640	16.26	S-1187	.41	10.3	.506	12.9	134	23	.12	3.0	16	70	.20	5.1	0.067	1.7	3.00	SST	CG	N
0.640	16.26	3181	.44	11.1	.512	13.0	126	22	.12	3.0	15	65	.19	4.9	0.064	1.6	3.00	SPR	CG	GI
0.640	16.26	10124	.50	12.7	.516	13.1	55	9.6	.19	4.8	10	46	.31	7.9	0.062	1.6	4.00	HD	C	Z
0.640	16.26	B15-27	.50	12.7	.500	12.7	110	19	.15	3.9	17	76	.25	6.2	0.070	1.8	3.50	SST	CG	N
0.640	16.26	3248	.63	15.9	.564	14.3	9.2	1.6	.37	9.3	3.4	15	.17	4.3	0.038	1.0	3.50	SPR	C	Z
0.640	16.26	S-1106	.63	15.9	.560	14.2	3.7	.65	.35	8.8	1.3	5.7	.28	7.1	0.040	1.0	6.00	SST	C	N
0.640	16.26	Q0-61	.69	17.4	.522	13.3	44	7.8	.26	6.6	12	51	.30	7.5	0.059	1.5	4.00	SPR	C	GI
0.640	16.26	3221	.69	17.4	.518	13.2	51	9.0	.25	6.3	13	57	.24	6.2	0.061	1.5	4.00	SPR	CG	GI
0.640	16.26	10595	.69	17.4	.430	10.9	368	64	.14	3.6	53	234	.50	12.7	0.105	2.7	4.75	SST	CG	N
0.640	16.26	S-889	.75	19.1	.542	13.8	9.2	1.6	.46	12	4.2	19	.29	7.3	0.049	1.2	6.00	SST	CG	N
0.640	16.26	KK-30	.75	19.1	.540	13.7	22	3.8	.32	8.2	7.1	32	.20	5.1	0.050	1.3	4.00	SPR	CG	Z
0.640	16.26	S-1428	.75	19.1	.430	10.9	397	70	.13	3.4	53	234	.47	12.0	0.105	2.7	4.50	SST	CG	N
0.640	16.26	BB-96	.84	21.4	.490	12.4	37	6.4	.24	6.2	8.9	40	.60	15.2	0.075	1.9	8.00	SST	CG	N
0.640	16.26	10134	.88	22.2	.512	13.0	42	7.4	.35	8.9	15	65	.32	8.1	0.064	1.6	5.00	SPR	CG	Z
0.640	16.26	10789	.88	22.2	.470	11.9	111	19	.27	6.9	30	134	.47	11.9	0.085	2.2	5.50	SST	CG	N
0.640	16.26	GG-94	.94	23.8	.532	13.5	13	2.3	.61	16	8.1	36	.32	8.2	0.054	1.4	6.00	SST	CG	N
0.640	16.26	MM-52	.94	23.8	.520	13.2	32	5.6	.38	9.7	12	54	.30	7.6	0.060	1.5	5.00	SPR	CG	Z
0.640	16.26	S-3197	.94	23.8	.468	11.9	117	21	.27	6.7	31	138	.47	12.0	0.086	2.2	5.50	SST	CG	N
0.640	16.26	10787	.97	24.6	.470	11.9	110	19	.29	7.4	32	143	.51	13.0	0.085	2.2	6.00	SPR	CG	N
0.640	16.26	UU-53	1.00	25.4	.550	14.0	7.0	1.2	.69	17	4.8	21	.32	8.0	0.045	1.1	6.00	SPR	C	Z
0.640	16.26	3144	1.00	25.4	.546	13.9	5.2	.91	.55	14	2.9	13	.45	11.3	0.047	1.2	8.50	SPR	C	Z
0.640	16.26	H-30	1.00	25.4	.528	13.4	18	3.1	.56	14	9.9	44	.34	8.5	0.056	1.4	6.00	SPR	CG	Z
0.640	16.26	2763	1.00	25.4	.474	12.0	175	31	.24	6.1	42	186	.44	11.1	0.083	2.1	4.25	MW	C	Z
0.640	16.26	S-1571	1.00	25.4	.468	11.9	126	22	.25	6.3	31	138	.45	11.5	0.086	2.2	5.25	SST	CG	N
0.640	16.26	A15-35	1.03	26.2	.548	13.9	11	1.9	.51	13	5.6	25	.21	5.3	0.046	1.2	4.50	SST	CG	N
0.640	16.26	GG-48	1.03	26.2	.520	13.2	19	3.3	.61	16	12	52	.42	10.7	0.060	1.5	7.00	SPR	CG	BO
0.640	16.26	2669	1.13	28.6	.396	10.1	688	120	.12	3.1	84	376	.77	19.6	0.122	3.1	5.33	SPR	C	Z
0.640	16.26	B7-58	1.16	29.4	.558	14.2	6.9	1.2	.61	16	4.2	19	.24	6.0	0.041	1.0	4.75	SPR	C	N
0.640	16.26	11901	1.16	29.4	.552	14.0	7.8	1.4	.66	17	5.2	23	.23	5.9	0.044	1.1	5.25	SPR	CG	N
0.640	16.26	A14-68	1.19	30.2	.548	13.9	8.4	1.5	.66	17	5.6	25	.29	7.3	0.046	1.2	5.25	SST	C	N
0.640	16.26	A14-69	1.19	30.2	.530	13.5	19	3.4	.46	12	8.8	39	.28	7.0	0.055	1.4	5.00	SST	CG	N
0.640	16.26	S-1248	1.19	30.2	.506	12.9	27	4.7	.59	15	16	70	.47	11.9	0.067	1.7	7.00	SST	CG	N
0.640	16.26	10240	1.25	31.8	.538	13.7	24	4.2	.32	8.0	7.5	33	.26	6.5	0.051	1.3	4.00	SPR	C	Z
0.640	16.26	11158	1.25	31.8	.528	13.4	18	3.1	.56	14	9.9	44	.34	8.5	0.056	1.4	6.00	SPR	CG	Z
0.640	16.26	10408	1.25	31.8	.516	13.1	31	5.5	.43	11	13	60	.34	8.7	0.062	1.6	5.50	SPR	CG	Z
0.640	16.26	3387	1.25	31.8	.480	12.2	56	9.8	.48	12	27	120	.64	16.3	0.080	2.0	8.00	SPR	CG	Z
0.640	16.26	A14-41	1.28	32.5	.530	13.5	18	3.1	.54	14	9.4	42	.32	8.0	0.055					




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.640	16.26	10335	2.00	50.8	.546	13.9	3.2	.56	1.4	36	4.5	20	.59	14.9	0.047	1.2	12.5	SPR	CG	Z
0.640	16.26	11750	2.00	50.8	.516	13.1	12	2.1	1.1	28	13	60	.68	17.3	0.062	1.6	11.0	SPR	CG	Z
0.640	16.26	12580	2.00	50.8	.480	12.2	36	6.3	.74	19	27	120	.98	24.9	0.080	2.0	11.3	SPR	CG	N
0.640	16.26	4316	2.13	54.0	.530	13.5	8.2	1.4	1.1	29	9.4	42	.55	14.0	0.055	1.4	10.0	SPR	CG	Z
0.640	16.26	S-321	2.19	55.6	.316	8.0	956	167	.16	4.1	156	693	1.66	42.2	0.162	4.1	10.3	SST	CG	N
0.640	16.26	3808	2.25	57.2	.430	10.9	104	18	.55	14	57	253	1.61	40.8	0.105	2.7	14.0	SPR	C	Z
0.640	16.26	LL-96	2.38	60.3	.480	12.2	30	5.2	.85	22	25	112	.96	24.4	0.080	2.0	12.0	SST	CG	N
0.640	16.26	2926	2.47	62.7	.532	13.5	6.1	1.1	1.5	37	8.9	40	.65	16.5	0.054	1.4	12.0	SPR	CG	Z
0.640	16.26	RR-11	2.50	63.5	.568	14.4	1.3	.23	2.1	53	2.7	12	.41	10.5	0.036	0.9	10.5	SPR	C	Z
0.640	16.26	10522	2.63	66.7	.516	13.1	10	1.8	1.3	34	13	60	.81	20.5	0.062	1.6	13.0	SPR	CG	Z
0.640	16.26	11374	2.63	66.7	.496	12.6	20	3.5	.91	23	18	82	.81	20.6	0.072	1.8	11.3	SST	CG	N
0.640	16.26	11596	2.69	68.2	.370	9.4	278	49	.39	10	109	485	2.20	56.0	0.135	3.4	15.3	SPR	CG	Z
0.640	16.26	2624	2.91	73.8	.430	10.9	71	12	.80	20	57	253	2.00	50.7	0.105	2.7	18.0	HD	C	Z
0.640	16.26	S-805	2.94	74.6	.558	14.2	1.6	.27	2.4	61	3.7	17	.55	14.1	0.041	1.0	12.5	SST	C	N
0.640	16.26	12455	3.00	76.2	.480	12.2	24	4.2	1.1	29	27	120	1.36	34.5	0.080	2.0	16.0	SPR	C	Z
0.640	16.26	S-3037	3.25	82.6	.430	10.9	58	10	.90	23	53	234	2.10	53.3	0.105	2.7	19.0	SST	C	N
0.640	16.26	10414	3.31	84.1	.430	10.9	67	12	.85	22	57	253	2.00	50.7	0.105	2.7	19.0	SPR	CG	Z
0.640	16.26	11800	3.50	88.9	.526	13.4	7.7	1.3	1.4	35	10	46	.74	18.8	0.057	1.4	12.0	SPR	C	Z
0.640	16.26	10771	4.00	101.6	.478	12.1	18	3.1	1.6	40	28	124	1.78	45.3	0.081	2.1	22.0	SPR	CG	GI
0.640	16.26	3437	4.50	114.3	.530	13.5	3.9	.68	2.4	62	9.4	42	1.10	27.9	0.055	1.4	19.0	SPR	C	Z
0.640	16.26	3154	4.50	114.3	.480	12.2	19	3.3	1.4	36	27	120	1.57	40.0	0.080	2.0	19.8	SPR	CG	Z
0.640	16.26	1593	4.88	123.8	.400	10.2	92	16	.87	22	81	358	3.00	76.2	0.120	3.0	25.0	SPR	CG	Z
0.640	16.26	3332	6.00	152.4	.496	12.6	5.2	.91	2.9	73	15	66	3.13	79.6	0.072	1.8	42.5	HD	C	Z
0.640	16.26	1531	8.00	203.2	.500	12.7	5.6	.98	3.2	82	18	81	2.54	64.5	0.070	1.8	35.3	SPR	C	Z
0.640	16.26	11691	9.75	247.7	.458	11.6	13	2.3	2.8	71	38	167	4.23	107.5	0.091	2.3	46.5	SPR	CG	GI
0.640	16.26	10152	11.0	279.4	.570	14.5	.28	.05	9.5	241	2.6	12	1.33	33.8	0.035	0.9	37.0	SPR	C	Z
0.653	16.59	12682	.69	17.4	.527	13.4	32	5.6	.31	7.8	9.9	44	.38	9.6	0.063	1.6	5.00	SST	C	N
0.656	16.66	10241	.34	8.7	.496	12.6	411	72	.06	1.6	26	117	.22	5.6	0.080	2.0	2.75	SPR	CG	Z
0.656	16.66	B4-70	.38	9.5	.600	15.2	3.1	.54	.26	6.7	.82	3.6	.11	2.8	0.028	0.7	3.00	SST	C	N
0.656	16.66	3645	.38	9.5	.574	14.6	17	3.1	.21	5.4	3.7	16	.16	4.2	0.041	1.0	3.00	HD	C	Z
0.656	16.66	11-97	.44	11.1	.574	14.6	15	2.7	.25	6.4	3.9	17	.16	4.2	0.041	1.0	3.00	SST	C	N
0.656	16.66	1763	.47	11.9	.562	14.3	18	3.1	.25	6.2	4.3	19	.22	5.7	0.047	1.2	3.75	HD	C	Z
0.656	16.66	S-883	.53	13.5	.546	13.9	28	4.9	.31	7.8	8.6	38	.21	5.4	0.055	1.4	4.00	SST	CG	N
0.656	16.66	12266	.56	14.3	.556	14.1	17	3.0	.35	8.8	6.0	27	.22	5.5	0.050	1.3	4.25	SPR	CG	Z
0.656	16.66	A-48	.66	16.7	.296	7.5	13992	2450	.02	.40	218	968	.54	13.7	0.180	4.6	3.00	HD	CG	Z
0.656	16.66	00-48	.69	17.4	.576	14.6	5.2	.92	.45	11	2.3	10	.24	6.1	0.040	1.0	5.00	SPR	C	GI
0.656	16.66	A11-28	.69	17.4	.560	14.2	15	2.6	.41	10	6.2	27	.19	4.9	0.048	1.2	4.00	SST	CG	N
0.656	16.66	S-1264	.69	17.4	.474	12.0	136	24	.19	4.7	25	113	.50	12.7	0.091	2.3	5.50	SST	CG	N
0.656	16.66	S-1210	.75	19.1	.574	14.6	7.6	1.3	.51	13	3.9	17	.21	5.2	0.041	1.0	4.00	SST	C	N
0.656	16.66	I-59	.75	19.1	.564	14.3	8.2	1.4	.52	13	4.3	19	.23	5.8	0.046	1.2	5.00	SST	CG	N
0.656	16.66	S-1403	.75	19.1	.532	13.5	44	7.7	.28	7.1	12	55	.25	6.3	0.062	1.6	4.00	SST	CG	N
0.656	16.66	A15-69	.75	19.1	.504	12.8	67	12	.32	8.0	21	94	.40	10.1	0.076	1.9	5.25	SST	CG	N
0.656	16.66	S-1135	.81	20.6	.592	15.0	2.4	.42	.64	16	1.5	6.9	.17	4.3	0.032	0.8	4.25	SST	C	N
0.656	16.66	S-479	.81	20.6	.544	13.8	24	4.3	.37	9.5	9.1	41	.24	6.2	0.056	1.4	4.25	SST	CG	N
0.656	16.66	B11-57	.84	21.4	.520	13.2	60	11	.28	7.2	17	76	.31	7.8	0.068	1.7	4.50	SPR	CG	Z
0.656	16.66	A14-64	1.00	25.4	.568	14.4	8.3	1.5	.57	14	4.8	21	.20	5.0	0.044	1.1	4.50	SST	CG	N
0.656	16.66	A14-52	1.00	25.4	.542	13.8	26	4.5	.40	10	10	45	.27	6.9	0.057	1.4	4.75	SPR	CG	GI
0.656	16.66	S-135	1.00	25.4	.512	13.0	42	7.4	.43	11	18	80	.50	12.8	0.072	1.8	6.00	SST	C	N
0.656	16.66	A14-63	1.03	26.2	.562	14.3	12	2.2	.50	13	6.2	27	.21	5.4	0.047	1.2	4.50	SPR	CG	GI
0.656	16.66	S-1391	1.03	26.2	.474	12.0	106	18	.32	8.2	34	152	.59	15.0	0.091	2.3	6.50	SST	CG	N
0.656	16.66	S-1102	1.06	27.0	.576	14.6	4.2	.74	.81	21	3.4	15	.25	6.4	0.040	1.0	5.25	SST	C	N
0.656	16.66	B9-57	1.06	27.0	.572	14.5	4.3	.75	.79	20	3.4	15	.27	6.9	0.042	1.1	6.50	SPR	CG	N
0.656	16.66	H-9	1.13	28.6	.562	14.3	10	1.8	.60	15	6.2	27	.24	6.0	0.047	1.2	5.00	SPR	CG	GI
0.656	16.66	10327	1.13	28.6	.548	13.9	12	2.2	.70	18	8.7	39	.41	10.3	0.054	1.4	6.50	SPR	C	Z
0.656	16.66	S-269	1.13	28.6	.548	13.9	13	2.3	.63	16	8.2	36	.36	9.3	0.054	1.4	5.75	SST	C	N
0.656	16.66	11228	1.13	28.6	.526	13.4	33	5.8	.45	12	15	67	.37	9.5	0.065	1.7	5.75	SPR	CG	Z
0.656	16.66	1601	1.13	28.6	.476	12.1	87	15	.41	10	35	156	.72	18.3	0.090	2.3	8.00	SPR	CG	Z
0.656	16.66	Y-26	1.13	28.6	.406	10.3	1172	205	.08	1.9	89	394	.50	12.7						



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.656	16.66	1715	1.75	44.5	.600	15.2	.55	.10	1.5	38	.81	3.6	.27	6.8	0.028	0.7	8.50	MW	C	Z
0.656	16.66	4186	1.75	44.5	.562	14.3	5.2	.91	1.2	30	6.2	27	.42	10.7	0.047	1.2	8.00	SPR	C	Z
0.656	16.66	A14-12	1.75	44.5	.396	10.1	316	55	.27	7.0	87	385	1.27	32.2	0.130	3.3	9.75	SST	CG	N
0.656	16.66	10157	1.78	45.2	.354	9.0	967	169	.15	3.7	142	634	1.21	30.7	0.151	3.8	8.00	SPR	CG	GI
0.656	16.66	S-1148	1.88	47.6	.432	11.0	122	21	.48	12	59	263	1.34	34.1	0.112	2.8	12.0	SST	CG	N
0.656	16.66	11882	1.91	48.4	.560	14.2	6.8	1.2	.97	25	6.6	29	.34	8.5	0.048	1.2	7.00	SPR	CG	N
0.656	16.66	11723	1.97	50.0	.552	14.0	7.9	1.4	.98	25	7.8	35	.42	10.6	0.052	1.3	8.00	SPR	CG	Z
0.656	16.66	B18-179	2.00	50.8	.576	14.6	1.7	.31	1.6	41	2.8	12	.40	10.2	0.040	1.0	10.0	SST	CG	N
0.656	16.66	4256	2.00	50.8	.560	14.2	6.5	1.1	1.0	26	6.6	29	.40	10.1	0.048	1.2	7.25	SPR	C	Z
0.656	16.66	11682	2.03	51.6	.530	13.5	12	2.1	1.1	29	14	61	.69	17.6	0.063	1.6	11.0	SPR	CG	Z
0.656	16.66	3130	2.06	52.4	.530	13.5	12	2.1	1.1	28	14	61	.69	17.4	0.063	1.6	11.0	SPR	CG	Z
0.656	16.66	2656	2.25	57.2	.546	13.9	6.2	1.1	1.5	38	9.2	41	.65	16.4	0.055	1.4	11.8	SPR	CG	Z
0.656	16.66	N-124	2.50	63.5	.574	14.6	1.9	.33	2.0	52	3.9	17	.45	11.5	0.041	1.0	10.0	SST	C	N
0.656	16.66	2514	2.53	64.3	.548	13.9	6.8	1.2	1.8	45	12	54	.55	14.1	0.054	1.4	10.3	MW	CG	Z
0.656	16.66	S-1121	2.63	66.7	.574	14.6	1.9	.33	2.0	52	3.9	17	.45	11.5	0.041	1.0	10.0	SST	C	N
0.656	16.66	11616	2.84	72.2	.414	10.5	161	28	.50	13	81	359	1.88	47.6	0.121	3.1	14.5	SPR	CG	Z
0.656	16.66	1635	2.88	73.0	.496	12.6	32	5.7	.81	21	26	117	1.00	25.4	0.080	2.0	11.5	SPR	C	Z
0.656	16.66	10997	3.06	77.8	.446	11.3	87	15	.64	16	56	247	1.47	37.3	0.105	2.7	14.0	HD	CG	Z
0.656	16.66	S-3179	3.31	84.1	.446	11.3	50	8.8	1.0	26	52	229	2.10	53.3	0.105	2.7	20.0	SST	CG	N
0.656	16.66	S-1525	3.50	88.9	.594	15.1	.29	.05	2.9	74	.83	3.7	.60	15.4	0.031	0.8	18.5	SST	C	N
0.656	16.66	11393	3.50	88.9	.562	14.3	2.3	.40	2.7	69	6.1	27	.79	20.0	0.047	1.2	15.8	HD	C	GI
0.656	16.66	11811	3.59	91.3	.428	10.9	85	15	.80	20	68	303	2.28	57.9	0.114	2.9	20.0	SPR	CG	Z
0.656	16.66	3337	4.00	101.6	.542	13.8	6.4	1.1	1.6	40	10	45	.80	20.3	0.057	1.4	13.0	SPR	C	Z
0.656	16.66	2684	4.94	125.4	.532	13.5	4.6	.80	2.9	73	13	58	1.57	39.8	0.062	1.6	24.3	HD	C	Z
0.656	16.66	4265	6.00	152.4	.532	13.5	2.7	.47	3.5	88	9.2	41	2.54	64.6	0.062	1.6	40.0	SPR	C	Z
0.656	16.66	1883	6.50	165.1	.532	13.5	3.4	.59	3.9	98	13	58	2.05	52.0	0.062	1.6	32.0	HD	C	Z
0.656	16.66	2805	6.63	168.3	.340	8.6	227	40	.71	18	161	717	5.37	136.4	0.158	4.0	34.0	HD	CG	Z
0.656	16.66	1825	7.75	196.9	.332	8.4	261	46	.66	17	172	767	5.43	137.8	0.162	4.1	33.5	HD	CG	Z
0.656	16.66	10289	9.50	241.3	.512	13.0	4.9	.86	3.9	100	19	86	3.06	77.7	0.072	1.8	41.5	SPR	C	Z
0.656	16.66	12116	11.1	281.8	.474	12.0	9.6	1.7	3.8	97	37	163	5.37	136.4	0.091	2.3	59.0	SPR	CG	Z
0.656	16.66	4019	18.5	469.9	.522	13.3	2.0	.35	8.2	209	16	73	4.96	125.9	0.067	1.7	73.0	HD	C	BO
0.660	16.76	71865	.63	16.0	.562	14.3	23	4.1	.41	10	9.6	43	.17	4.4	0.049	1.2	3.50	MW	CG	N
0.660	16.76	71865S	.63	16.0	.562	14.3	20	3.5	.33	8.3	6.5	29	.17	4.4	0.049	1.2	3.50	SST	CG	N
0.660	16.76	71877	.63	16.0	.550	14.0	36	6.3	.35	8.9	13	56	.20	5.1	0.055	1.4	3.63	MW	CG	N
0.660	16.76	71877S	.63	16.0	.550	14.0	31	5.4	.28	7.1	8.6	38	.20	5.1	0.055	1.4	3.63	SST	CG	N
0.660	16.76	71889	.63	16.0	.534	13.6	56	9.7	.34	8.6	19	84	.24	6.2	0.063	1.6	3.88	MW	CG	N
0.660	16.76	71889S	.63	16.0	.534	13.6	47	8.3	.27	6.9	13	57	.24	6.2	0.063	1.6	3.88	SST	CG	N
0.660	16.76	71901	.63	16.0	.526	13.4	71	12	.32	8.2	23	101	.27	6.8	0.067	1.7	4.00	MW	CG	N
0.660	16.76	71901S	.63	16.0	.526	13.4	60	11	.26	6.5	15	68	.27	6.8	0.067	1.7	4.00	SST	CG	N
0.660	16.76	71913	.63	16.0	.516	13.1	94	16	.28	7.2	27	119	.29	7.3	0.072	1.8	4.00	MW	CG	N
0.660	16.76	71913S	.63	16.0	.516	13.1	80	14	.22	5.7	18	80	.29	7.3	0.072	1.8	4.00	SST	CG	N
0.660	16.76	71866	.75	19.1	.562	14.3	18	3.2	.53	13	9.6	43	.20	5.0	0.049	1.2	4.00	MW	CG	N
0.660	16.76	71866S	.75	19.1	.562	14.3	15	2.7	.42	11	6.5	29	.20	5.0	0.049	1.2	4.00	SST	CG	N
0.660	16.76	71878	.75	19.1	.550	14.0	29	5.1	.44	11	13	56	.22	5.6	0.055	1.4	4.00	MW	CG	N
0.660	16.76	71878S	.75	19.1	.550	14.0	25	4.3	.35	8.9	8.6	38	.22	5.6	0.055	1.4	4.00	SST	CG	N
0.660	16.76	71890	.75	19.1	.534	13.6	45	7.8	.43	11	19	84	.28	7.0	0.063	1.6	4.38	MW	CG	N
0.660	16.76	71890S	.75	19.1	.534	13.6	38	6.6	.34	8.6	13	57	.28	7.0	0.063	1.6	4.38	SST	CG	N
0.660	16.76	71902	.75	19.1	.526	13.4	56	9.9	.40	10	23	101	.30	7.7	0.067	1.7	4.50	MW	CG	N
0.660	16.76	71902S	.75	19.1	.526	13.4	48	8.4	.32	8.1	15	68	.30	7.7	0.067	1.7	4.50	SST	CG	N
0.660	16.76	71914	.75	19.1	.516	13.1	75	13	.36	9.1	27	119	.32	8.2	0.072	1.8	4.50	MW	CG	N
0.660	16.76	71914S	.75	19.1	.516	13.1	63	11	.28	7.2	18	80	.32	8.2	0.072	1.8	4.50	SST	CG	N
0.660	16.76	71867	.88	22.4	.562	14.3	15	2.7	.63	16	9.6	43	.21	5.4	0.049	1.2	4.38	MW	CG	N
0.660	16.76	71867S	.88	22.4	.562	14.3	13	2.3	.50	13	6.5	29	.21	5.4	0.049	1.2	4.38	SST	CG	N
0.660	16.76	71879	.88	22.4	.550	14.0	24	4.2	.53	13	13	56	.25	6.3	0.055	1.4	4.50	MW	CG	N
0.660	16.76	71879S	.88	22.4	.550	14.0	20	3.6	.42	11	8.6	38	.25	6.3	0.055	1.4	4.50	SST	CG	N
0.660	16.76	71891	.88	22.4	.534	13.6	37	6.5	.51	13	19	84	.31	7.8	0.063	1.6	4.88	MW	CG	N
0.660	16.76	71891S	.88	22.4	.534	13.6	32	5.5	.41	10	13	57	.31	7.8	0.063	1.6	4			




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.660	16.76	71917S	1.25	31.8	.516	13.1	35	6.1	.52	13	18	80	.48	12.1	0.072	1.8	6.63	SST	CG	N
0.660	16.76	71870	1.50	38.1	.562	14.3	8.5	1.5	1.1	29	9.6	43	.31	7.8	0.049	1.2	6.25	MW	CG	N
0.660	16.76	71870S	1.50	38.1	.562	14.3	7.2	1.3	.90	23	6.5	29	.31	7.8	0.049	1.2	6.25	SST	CG	N
0.660	16.76	71882	1.50	38.1	.550	14.0	13	2.3	.95	24	13	56	.36	9.1	0.055	1.4	6.50	MW	CG	N
0.660	16.76	71882S	1.50	38.1	.550	14.0	11	2.0	.76	19	8.6	38	.36	9.1	0.055	1.4	6.50	SST	CG	N
0.660	16.76	71894	1.50	38.1	.534	13.6	20	3.5	.94	24	19	84	.46	11.6	0.063	1.6	7.25	MW	CG	N
0.660	16.76	71894S	1.50	38.1	.534	13.6	17	3.0	.75	19	13	57	.46	11.6	0.063	1.6	7.25	SST	CG	N
0.660	16.76	71906	1.50	38.1	.526	13.4	26	4.5	.89	23	23	101	.50	12.8	0.067	1.7	7.50	MW	CG	N
0.660	16.76	71906S	1.50	38.1	.526	13.4	22	3.8	.71	18	15	68	.50	12.8	0.067	1.7	7.50	SST	CG	N
0.660	16.76	71918	1.50	38.1	.516	13.1	34	5.9	.80	20	27	119	.55	13.9	0.072	1.8	7.63	MW	CG	N
0.660	16.76	71918S	1.50	38.1	.516	13.1	28	5.0	.63	16	18	80	.55	13.9	0.072	1.8	7.63	SST	CG	N
0.660	16.76	71871	1.75	44.5	.562	14.3	7.2	1.3	1.3	34	9.6	43	.34	8.7	0.049	1.2	7.00	MW	CG	N
0.660	16.76	71871S	1.75	44.5	.562	14.3	6.1	1.1	1.1	27	6.5	29	.34	8.7	0.049	1.2	7.00	SST	CG	N
0.660	16.76	71883	1.75	44.5	.550	14.0	11	2.0	1.1	28	13	56	.40	10.1	0.055	1.4	7.25	MW	CG	N
0.660	16.76	71883S	1.75	44.5	.550	14.0	9.6	1.7	.89	23	8.6	38	.40	10.1	0.055	1.4	7.25	SST	CG	N
0.660	16.76	71895	1.75	44.5	.534	13.6	17	3.0	1.1	28	19	84	.52	13.2	0.063	1.6	8.25	MW	CG	N
0.660	16.76	71895S	1.75	44.5	.534	13.6	15	2.5	.88	22	13	57	.52	13.2	0.063	1.6	8.25	SST	CG	N
0.660	16.76	71907	1.75	44.5	.526	13.4	22	3.8	1.1	27	23	101	.57	14.5	0.067	1.7	8.50	MW	CG	N
0.660	16.76	71907S	1.75	44.5	.526	13.4	18	3.2	.84	21	15	68	.57	14.5	0.067	1.7	8.50	SST	CG	N
0.660	16.76	71919	1.75	44.5	.516	13.1	28	4.9	.95	24	27	119	.63	16.0	0.072	1.8	8.75	MW	CG	N
0.660	16.76	71919S	1.75	44.5	.516	13.1	24	4.2	.75	19	18	80	.63	16.0	0.072	1.8	8.75	SST	CG	N
0.660	16.76	71872	2.00	50.8	.562	14.3	6.3	1.1	1.5	39	9.6	43	.39	9.8	0.049	1.2	7.88	MW	CG	N
0.660	16.76	71872S	2.00	50.8	.562	14.3	5.3	.93	1.2	31	6.5	29	.39	9.8	0.049	1.2	7.88	SST	CG	N
0.660	16.76	71884	2.00	50.8	.550	14.0	9.8	1.7	1.3	33	13	56	.44	11.2	0.055	1.4	8.00	MW	CG	N
0.660	16.76	71884S	2.00	50.8	.550	14.0	8.3	1.5	1.0	26	8.6	38	.44	11.2	0.055	1.4	8.00	SST	CG	N
0.660	16.76	71896	2.00	50.8	.534	13.6	15	2.6	1.3	32	19	84	.58	14.8	0.063	1.6	9.25	MW	CG	N
0.660	16.76	71896S	2.00	50.8	.534	13.6	13	2.2	1.0	26	13	57	.58	14.8	0.063	1.6	9.25	SST	CG	N
0.660	16.76	71908	2.00	50.8	.526	13.4	19	3.3	1.2	31	23	101	.64	16.2	0.067	1.7	9.50	MW	CG	N
0.660	16.76	71908S	2.00	50.8	.526	13.4	16	2.8	.97	25	15	68	.64	16.2	0.067	1.7	9.50	SST	CG	N
0.660	16.76	71920	2.00	50.8	.516	13.1	25	4.3	1.1	28	27	119	.70	17.8	0.072	1.8	9.75	MW	CG	N
0.660	16.76	71920S	2.00	50.8	.516	13.1	21	3.6	.86	22	18	80	.70	17.8	0.072	1.8	9.75	SST	CG	N
0.660	16.76	71873	2.25	57.2	.562	14.3	5.5	.96	1.7	44	9.6	43	.42	10.7	0.049	1.2	8.63	MW	CG	N
0.660	16.76	71873S	2.25	57.2	.562	14.3	4.7	.82	1.4	35	6.5	29	.42	10.7	0.049	1.2	8.63	SST	CG	N
0.660	16.76	71885	2.25	57.2	.550	14.0	8.6	1.5	1.5	37	13	56	.49	12.4	0.055	1.4	8.88	MW	CG	N
0.660	16.76	71885S	2.25	57.2	.550	14.0	7.3	1.3	1.2	30	8.6	38	.49	12.4	0.055	1.4	8.88	SST	CG	N
0.660	16.76	71897	2.25	57.2	.534	13.6	13	2.3	1.4	37	19	84	.64	16.2	0.063	1.6	10.1	MW	CG	N
0.660	16.76	71897S	2.25	57.2	.534	13.6	11	1.9	1.2	29	13	57	.64	16.2	0.063	1.6	10.1	SST	CG	N
0.660	16.76	71909	2.25	57.2	.526	13.4	17	2.9	1.4	35	23	101	.70	17.7	0.067	1.7	10.4	MW	CG	N
0.660	16.76	71909S	2.25	57.2	.526	13.4	14	2.5	1.1	28	15	68	.70	17.7	0.067	1.7	10.4	SST	CG	N
0.660	16.76	71921	2.25	57.2	.516	13.1	22	3.8	1.2	32	27	119	.78	19.9	0.072	1.8	10.9	MW	CG	N
0.660	16.76	71921S	2.25	57.2	.516	13.1	18	3.2	.98	25	18	80	.78	19.9	0.072	1.8	10.9	SST	CG	N
0.660	16.76	71874	2.50	63.5	.562	14.3	5.0	.87	1.9	49	9.6	43	.46	11.7	0.049	1.2	9.38	MW	CG	N
0.660	16.76	71874S	2.50	63.5	.562	14.3	4.2	.74	1.5	39	6.5	29	.46	11.7	0.049	1.2	9.38	SST	CG	N
0.660	16.76	71886	2.50	63.5	.550	14.0	7.8	1.4	1.6	42	13	56	.53	13.4	0.055	1.4	9.63	MW	CG	N
0.660	16.76	71886S	2.50	63.5	.550	14.0	6.6	1.2	1.3	33	8.6	38	.53	13.4	0.055	1.4	9.63	SST	CG	N
0.660	16.76	71898	2.50	63.5	.534	13.6	12	2.0	1.6	41	19	84	.70	17.8	0.063	1.6	11.1	MW	CG	N
0.660	16.76	71898S	2.50	63.5	.534	13.6	9.9	1.7	1.3	33	13	57	.70	17.8	0.063	1.6	11.1	SST	CG	N
0.660	16.76	71910	2.50	63.5	.526	13.4	15	2.6	1.5	39	23	101	.77	19.6	0.067	1.7	11.5	MW	CG	N
0.660	16.76	71910S	2.50	63.5	.526	13.4	12	2.2	1.2	31	15	68	.77	19.6	0.067	1.7	11.5	SST	CG	N
0.660	16.76	71922	2.50	63.5	.516	13.1	19	3.4	1.4	35	27	119	.86	21.7	0.072	1.8	11.9	MW	CG	N
0.660	16.76	71922S	2.50	63.5	.516	13.1	16	2.9	1.1	28	18	80	.86	21.7	0.072	1.8	11.9	SST	CG	N
0.660	16.76	71875	2.75	69.9	.562	14.3	4.5	.79	2.1	54	9.6	43	.50	12.6	0.049	1.2	10.1	MW	CG	N
0.660	16.76	71875S	2.75	69.9	.562	14.3	3.8	.67	1.7	43	6.5	29	.50	12.6	0.049	1.2	10.1	SST	CG	N
0.660	16.76	71887	2.75	69.9	.550	14.0	7.0	1.2	1.8	46	13	56	.58	14.7	0.055	1.4	10.5	MW	CG	N
0.660	16.76	71887S	2.75	69.9	.550	14.0	6.0	1.0	1.4	37	8.6	38	.58	14.7	0.055	1.4	10.5	SST	CG	N
0.660	16.76	71899	2.75	69.9	.534	13.6	11	1.9	1.8	45	19	84	.76	19.2	0.063	1.6	12.0	MW	CG	N
0.660	16.76	71899S	2.75	69.9	.534	13.6	9.0	1.6	1.4	36	13	57	.76	19.2	0.063	1.6	12.0	SST	CG	N
0.66																				




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.671	17.04	K-59A	.88	22.2	.543	13.8	31	5.4	.46	12	14	63	.42	10.6	0.064	1.6	5.50	SPR	C	Z
0.671	17.04	N-127	.88	22.2	.487	12.4	134	24	.26	6.5	34	153	.51	12.9	0.092	2.3	5.50	SST	CG	N
0.671	17.04	XX-19	.94	23.8	.561	14.2	9.4	1.6	.44	11	4.2	18	.50	12.6	0.055	1.4	8.00	SPR	C	Z
0.671	17.04	10010	1.06	27.0	.527	13.4	42	7.4	.45	11	19	84	.52	13.3	0.072	1.8	6.25	HD	C	Z
0.671	17.04	B7-70	1.09	27.8	.603	15.3	1.5	.26	.86	22	1.3	5.7	.24	6.0	0.034	0.9	7.00	SPR	CG	N
0.671	17.04	10467	1.13	28.6	.611	15.5	1.0	.18	.91	23	.94	4.2	.22	5.5	0.030	0.8	6.25	MW	C	Z
0.671	17.04	RR-66	1.13	28.6	.563	14.3	9.1	1.6	.75	19	6.8	30	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.671	17.04	BB-66	1.13	28.6	.511	13.0	51	8.9	.48	12	24	107	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.671	17.04	3758	1.13	28.6	.451	11.5	207	36	.27	6.9	56	251	.85	21.7	0.110	2.8	7.75	SPR	CG	Z
0.671	17.04	10725	1.19	30.2	.537	13.6	33	5.8	.49	12	16	72	.40	10.2	0.067	1.7	6.00	SPR	CG	GI
0.671	17.04	11316	1.19	30.2	.511	13.0	63	11	.41	10	26	114	.52	13.2	0.080	2.0	6.50	SPR	CG	Z
0.671	17.04	S-784	1.25	31.8	.589	15.0	3.5	.62	1.0	26	3.5	16	.25	6.2	0.041	1.0	6.00	SST	CG	N
0.671	17.04	2999	1.25	31.8	.563	14.3	11	1.9	.78	20	8.5	38	.36	9.3	0.054	1.4	6.75	SPR	CG	Z
0.671	17.04	J-38	1.25	31.8	.563	14.3	9.5	1.7	.84	21	8.0	36	.36	9.3	0.054	1.4	6.75	SST	CG	N
0.671	17.04	4270	1.25	31.8	.555	14.1	8.6	1.5	.60	15	5.1	23	.65	16.6	0.058	1.5	10.3	SPR	C	Z
0.671	17.04	3275	1.25	31.8	.487	12.4	106	19	.35	8.9	37	165	.74	18.7	0.092	2.3	7.00	SPR	C	Z
0.671	17.04	12582	1.30	32.9	.475	12.1	141	25	.32	8.0	45	199	.78	19.9	0.098	2.5	7.00	SPR	C	N
0.671	17.04	10837	1.44	36.5	.607	15.4	1.3	.22	1.2	30	1.5	6.8	.24	6.1	0.032	0.8	6.50	SPR	C	Z
0.671	17.04	4262	1.44	36.5	.527	13.4	40	7.0	.47	12	19	84	.47	11.9	0.072	1.8	6.50	SPR	CG	Z
0.671	17.04	S-786	1.50	38.1	.563	14.3	9.1	1.6	.88	22	8.0	36	.43	11.0	0.054	1.4	7.00	SST	C	N
0.671	17.04	2577	1.50	38.1	.561	14.2	8.3	1.5	1.0	26	8.5	38	.48	12.2	0.055	1.4	8.75	MW	CG	GI
0.671	17.04	2858	1.50	38.1	.561	14.2	8.3	1.5	1.0	26	8.5	38	.48	12.2	0.055	1.4	8.75	MW	CG	GI
0.671	17.04	2693	1.50	38.1	.527	13.4	31	5.5	.84	21	26	117	.56	14.2	0.072	1.8	7.75	MW	CG	GI
0.671	17.04	S-1468	1.50	38.1	.511	13.0	41	7.2	.58	15	24	107	.64	16.3	0.080	2.0	8.00	SST	CG	N
0.671	17.04	10701	1.50	38.1	.489	12.4	72	13	.50	13	36	160	.82	20.8	0.091	2.3	9.00	SPR	CG	Z
0.671	17.04	B10-69	1.56	39.7	.601	15.3	1.3	.23	1.3	32	1.6	7.3	.30	7.6	0.035	0.9	8.50	SPR	CG	Z
0.671	17.04	O-116	1.56	39.7	.563	14.3	5.8	1.0	.91	23	5.3	24	.65	16.5	0.054	1.4	11.0	SPR	C	Z
0.671	17.04	10757	1.56	39.7	.467	11.9	109	19	.46	12	50	223	.99	25.3	0.102	2.6	9.75	SPR	CG	N
0.671	17.04	11703	1.59	40.5	.561	14.2	9.4	1.6	.96	24	9.0	40	.44	11.2	0.055	1.4	8.00	SPR	CG	Z
0.671	17.04	3319	1.63	41.3	.511	13.0	29	5.0	.67	17	19	84	.96	24.4	0.080	2.0	12.0	SPR	CG	Z
0.671	17.04	S-104	1.69	42.8	.431	10.9	226	40	.31	7.9	71	314	1.08	27.4	0.120	3.0	9.00	SST	CG	N
0.671	17.04	B2-61	1.73	43.9	.563	14.3	12	2.0	.74	19	8.5	38	.41	10.3	0.054	1.4	6.50	SPR	C	GI
0.671	17.04	S-13	1.75	44.5	.577	14.7	4.6	.80	1.2	31	5.7	25	.40	10.1	0.047	1.2	7.50	SST	C	N
0.671	17.04	3893	1.75	44.5	.543	13.8	13	2.4	1.0	26	14	63	.70	17.9	0.064	1.6	10.0	SPR	C	Z
0.671	17.04	3698	1.81	46.0	.559	14.2	7.6	1.3	1.2	30	9.1	40	.62	15.6	0.056	1.4	10.0	SPR	C	Z
0.671	17.04	10682	1.84	46.8	.447	11.4	167	29	.38	9.7	64	283	1.09	27.7	0.112	2.8	9.75	SPR	CG	Z
0.671	17.04	10545	1.84	46.8	.441	11.2	183	32	.37	9.5	69	305	1.15	29.2	0.115	2.9	10.0	SPR	CG	Z
0.671	17.04	25	1.88	47.6	.511	13.0	30	5.3	.86	22	26	114	1.00	25.4	0.080	2.0	11.5	HD	C	Z
0.671	17.04	10357	1.88	47.6	.431	10.9	210	37	.37	9.4	77	344	1.26	32.0	0.120	3.0	10.5	SPR	CG	Z
0.671	17.04	S-1541	1.91	48.4	.583	14.8	1.9	.33	1.4	35	2.6	12	.53	13.4	0.044	1.1	12.0	SST	CG	N
0.671	17.04	S-360	1.91	48.4	.511	13.0	31	5.4	.78	20	24	107	.80	20.3	0.080	2.0	10.0	SST	CG	N
0.671	17.04	12518	1.94	49.2	.447	11.4	162	28	.39	10	64	283	1.23	31.3	0.112	2.8	10.0	SPR	C	N
0.671	17.04	S-64	2.00	50.8	.577	14.7	3.3	.59	1.6	39	5.2	23	.45	11.3	0.047	1.2	9.50	SST	CG	N
0.671	17.04	12086	2.00	50.8	.541	13.7	8.0	1.4	.93	24	7.4	33	1.07	27.2	0.065	1.7	16.5	SPR	CG	Z
0.671	17.04	12183	2.03	51.6	.517	13.1	24	4.2	.95	24	23	102	.92	23.5	0.077	2.0	12.0	SPR	CG	GI
0.671	17.04	10235	2.13	54.0	.445	11.3	135	24	.48	12	65	290	1.36	34.4	0.113	2.9	12.0	SPR	CG	GI
0.671	17.04	3036	2.22	56.4	.547	13.9	9.4	1.6	1.4	35	13	57	.74	18.9	0.062	1.6	12.0	SPR	CG	Z
0.671	17.04	B-20	2.31	58.7	.581	14.8	2.5	.44	1.8	46	4.5	20	.52	13.1	0.045	1.1	11.5	HD	CG	Z
0.671	17.04	12598	2.50	63.5	.581	14.8	2.7	.47	2.0	51	5.4	24	.50	12.6	0.045	1.1	11.0	MW	CG	N
0.671	17.04	11662	2.53	64.3	.563	14.3	5.2	.91	1.6	42	8.5	38	.65	16.5	0.054	1.4	12.0	SPR	CG	Z
0.671	17.04	S-808	2.56	65.1	.419	10.6	166	29	.49	12	81	361	1.73	44.0	0.126	3.2	13.8	SST	CG	N
0.671	17.04	4209	2.58	65.5	.569	14.5	8.2	1.4	.88	22	7.2	32	.41	10.4	0.051	1.3	7.00	SPR	CG	N
0.671	17.04	10562	2.91	73.8	.483	12.3	44	7.7	.90	23	40	176	1.53	38.8	0.094	2.4	15.3	SPR	C	Z
0.671	17.04	11744	3.00	76.2	.551	14.0	7.1	1.2	1.6	42	12	52	.87	22.1	0.060	1.5	13.5	SPR	C	Z
0.671	17.04	S-1363	3.31	84.1	.589	15.0	1.3	.24	2.8	71	3.8	17	.51	13.0	0.041	1.0	12.5	SST	CG	N
0.671	17.04	2613	3.50	88.9	.541	13.7	7.4	1.3	2.0	51	15	65	1.15	29.1	0.065	1.7	17.5	HD	CG	Z
0.671	17.04	11351	4.25	108.0	.611	15.5	.24	.04	3.7	14	.89	3.								



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F W S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.687	17.45	3949	.94	23.8	.563	14.3	18	3.2	.46	12	8.4	37	.48	12.2	0.062	1.6	6.75	SPR	C	Z
0.687	17.45	S-800	.97	24.6	.617	15.7	2.3	.40	.79	20	1.8	8.0	.18	4.4	0.035	0.9	5.00	SST	CG	N
0.687	17.45	12332	.97	24.6	.605	15.4	7.5	1.3	.52	13	3.9	18	.21	5.2	0.041	1.0	4.00	SPR	C	Z
0.687	17.45	11105	1.00	25.4	.617	15.7	3.1	.55	.81	21	2.5	11	.19	4.9	0.035	0.9	4.50	MW	C	Z
0.687	17.45	3654	1.00	25.4	.595	15.1	6.1	1.1	.72	18	4.4	20	.28	7.0	0.046	1.2	6.00	SPR	CG	Z
0.687	17.45	11345	1.00	25.4	.579	14.7	8.5	1.5	.62	16	5.3	24	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.687	17.45	3349	1.00	25.4	.573	14.6	14	2.5	.59	15	8.4	37	.41	10.5	0.057	1.4	6.25	HD	C	Z
0.687	17.45	3350	1.00	25.4	.571	14.5	15	2.5	.57	14	8.2	37	.44	11.0	0.058	1.5	6.50	SPR	C	Z
0.687	17.45	12148	1.00	25.4	.501	12.7	128	22	.29	7.4	38	167	.56	14.2	0.093	2.4	6.00	SPR	CG	Z
0.687	17.45	3943	1.00	25.4	.363	9.2	2281	399	.07	1.9	167	742	.81	20.6	0.162	4.1	5.00	SPR	CG	Z
0.687	17.45	MM-93	1.00	25.4	.307	7.8	5087	891	.05	1.2	244	1084	.95	24.1	0.190	4.8	5.00	SPR	CG	N
0.687	17.45	1950	1.03	26.2	.603	15.3	8.3	1.5	.51	13	4.2	19	.21	5.3	0.042	1.1	4.00	SPR	C	Z
0.687	17.45	AA-82	1.03	26.2	.547	13.9	43	7.6	.37	9.3	16	71	.42	10.7	0.070	1.8	5.00	SST	C	N
0.687	17.45	B5-38	1.09	27.8	.605	15.4	6.7	1.2	.59	15	3.9	18	.22	5.5	0.041	1.0	4.25	SPR	C	N
0.687	17.45	S-1291	1.13	28.6	.579	14.7	14	2.4	.56	14	7.8	35	.27	6.9	0.054	1.4	5.00	SST	CG	N
0.687	17.45	4117	1.13	28.6	.527	13.4	66	12	.38	9.7	25	112	.48	12.2	0.080	2.0	6.00	SPR	CG	Z
0.687	17.45	4221	1.13	28.6	.519	13.2	82	14	.36	9.0	29	129	.50	12.8	0.084	2.1	6.00	SPR	CG	Z
0.687	17.45	10079	1.13	28.6	.431	10.9	631	111	.14	3.7	91	406	.70	17.9	0.128	3.3	5.50	SPR	CG	Z
0.687	17.45	K-15	1.19	30.2	.579	14.7	7.1	1.2	.70	18	5.0	22	.49	12.3	0.054	1.4	8.00	SST	C	N
0.687	17.45	11312	1.19	30.2	.511	13.0	95	17	.33	8.3	31	139	.51	12.9	0.088	2.2	5.75	SST	CG	N
0.687	17.45	S-1624	1.22	31.0	.607	15.4	3.0	.53	.98	25	2.9	13	.24	6.1	0.040	1.0	6.00	SST	CG	N
0.687	17.45	11707	1.22	31.0	.569	14.5	13	2.2	.78	20	9.9	44	.44	11.2	0.059	1.5	7.50	SPR	CG	Z
0.687	17.45	S-961	1.22	31.0	.561	14.2	20	3.5	.61	15	12	55	.38	9.6	0.063	1.6	6.00	SST	CG	N
0.687	17.45	3114	1.25	31.8	.579	14.7	11	1.9	.75	19	8.3	37	.40	10.1	0.054	1.4	6.25	SPR	C	Z
0.687	17.45	Z-41	1.25	31.8	.579	14.7	8.4	1.5	.87	22	7.3	33	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.687	17.45	S-1471	1.25	31.8	.563	14.3	19	3.3	.62	16	12	52	.37	9.4	0.062	1.6	6.00	SST	CG	N
0.687	17.45	I-32	1.25	31.8	.559	14.2	20	3.5	.69	18	14	61	.45	11.4	0.064	1.6	7.00	SPR	CG	Z
0.687	17.45	10295	1.25	31.8	.557	14.1	28	5.0	.51	13	14	64	.37	9.5	0.065	1.7	5.75	SPR	CG	Z
0.687	17.45	505	1.25	31.8	.543	13.8	39	6.8	.47	12	18	82	.52	13.3	0.072	1.8	6.25	HD	C	Z
0.687	17.45	B8-58	1.25	31.8	.537	13.6	35	6.2	.55	14	20	87	.53	13.3	0.075	1.9	7.00	SST	CG	N
0.687	17.45	28	1.25	31.8	.505	12.8	89	16	.40	10	35	157	.75	19.1	0.091	2.3	7.25	HD	C	Z
0.687	17.45	11192	1.31	33.3	.505	12.8	67	12	.49	13	33	146	.82	20.8	0.091	2.3	9.00	HD	CG	Z
0.687	17.45	11680	1.31	33.3	.461	11.7	248	43	.26	6.5	64	284	.79	20.1	0.113	2.9	7.00	SPR	CG	Z
0.687	17.45	12025	1.34	34.1	.481	12.2	162	28	.31	7.9	50	225	.82	20.9	0.103	2.6	7.00	SPR	C	Z
0.687	17.45	11367	1.38	34.9	.527	13.4	41	7.1	.58	15	24	105	.62	15.7	0.080	2.0	7.75	SST	CG	N
0.687	17.45	EE-94	1.38	34.9	.447	11.4	327	57	.23	5.9	76	337	.84	21.3	0.120	3.0	7.00	SPR	CG	Z
0.687	17.45	S-267	1.44	36.5	.623	15.8		.12	1.2	29	.77	3.4	.29	7.3	0.032	0.8	9.00	SST	CG	N
0.687	17.45	S-950	1.44	36.5	.601	15.3	3.8	.66	1.1	29	4.2	19	.27	6.8	0.043	1.1	6.25	SST	CG	N
0.687	17.45	S-1004	1.50	38.1	.607	15.4	2.4	.41	1.2	31	2.9	13	.28	7.1	0.040	1.0	7.00	SST	CG	N
0.687	17.45	S-1357	1.50	38.1	.605	15.4	4.0	.71	.91	23	3.7	16	.22	5.5	0.041	1.0	5.25	SST	CG	N
0.687	17.45	S-1424	1.50	38.1	.585	14.9	8.2	1.4	.80	20	6.6	29	.36	9.1	0.051	1.3	6.00	SST	C	N
0.687	17.45	2734	1.50	38.1	.561	14.2	21	3.6	.88	22	18	81	.41	10.4	0.063	1.6	6.50	MW	CG	GI
0.687	17.45	S-1387	1.50	38.1	.553	14.0	21	3.7	.70	18	15	66	.47	11.9	0.067	1.7	7.00	SST	CG	N
0.687	17.45	B9-49	1.50	38.1	.551	14.0	26	4.5	.63	16	16	73	.48	12.1	0.068	1.7	7.00	SPR	CG	N
0.687	17.45	11537	1.50	38.1	.543	13.8	28	4.8	.67	17	18	82	.65	16.5	0.072	1.8	8.00	SPR	C	Z
0.687	17.45	11649	1.50	38.1	.537	13.6	33	5.8	.63	16	21	93	.60	15.2	0.075	1.9	8.00	SPR	CG	GI
0.687	17.45	11611	1.50	38.1	.517	13.1	69	12	.44	11	30	134	.68	17.3	0.085	2.2	7.00	SPR	CG	Z
0.687	17.45	A-64	1.50	38.1	.477	12.1	118	21	.45	11	53	237	1.00	25.3	0.105	2.7	9.50	SPR	CG	N
0.687	17.45	2910	1.50	38.1	.447	11.4	252	44	.30	7.7	76	337	1.02	25.9	0.120	3.0	8.50	SPR	CG	Z
0.687	17.45	S-276	1.50	38.1	.447	11.4	219	38	.32	8.0	69	308	1.02	25.9	0.120	3.0	8.50	SST	CG	N
0.687	17.45	KK-75	1.53	38.9	.507	12.9	42	7.3	.81	21	34	152	.70	17.7	0.090	2.3	7.75	PB	CG	N
0.687	17.45	1917	1.56	39.7	.497	12.6	87	15	.46	12	40	178	.81	20.5	0.095	2.4	8.50	SPR	CG	Z
0.687	17.45	12172	1.63	41.3	.567	14.4	7.6	1.3	.91	23	6.8	30	.72	18.3	0.060	1.5	12.0	SPR	CG	Z
0.687	17.45	B9-54	1.63	41.3	.545	13.8	31	5.5	.57	14	18	79	.57	14.4	0.071	1.8	7.00	SPR	C	N
0.687	17.45	S-3107	1.63	41.3	.503	12.8	61	11	.56	14	34	150	.92	23.4	0.092	2.3	9.00	SST	C	N
0.687	17.45	12099	1.63	41.3	.475	12.1	103	18	.46	12	47	210	1.17	29.6	0.106	2.7	11.0	SPR	CG	Z
0.687	17.45	AA-62	1.63	41.3	.427	10.8	380	67	.24	6.2	93	412	1.07	27.2	0.130	3.3	8.25	SPR	CG	N
0.687	17.45	11559	1.69	42.8	.565	14.4	12	2.0	1											



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.687	17.45	B8-43	2.38	60.3	.569	14.5	4.5	.78	1.4	36	6.4	28	.94	24.0	0.059	1.5	16.0	SST	CG	N
0.687	17.45	11984	2.38	60.3	.511	13.0	43	7.5	.77	20	33	148	1.00	25.3	0.088	2.2	11.3	SPR	CG	Z
0.687	17.45	11972	2.41	61.1	.565	14.4	6.8	1.2	1.6	39	10	47	.85	21.7	0.061	1.5	14.0	SPR	CG	Z
0.687	17.45	11296	2.50	63.5	.611	15.5	.93	.16	1.9	49	1.8	8.1	.56	14.2	0.038	1.0	13.8	MW	C	Z
0.687	17.45	S-372	2.50	63.5	.575	14.6	4.6	.80	1.8	45	8.2	37	.71	18.0	0.056	1.4	12.7	SST	CG	N
0.687	17.45	S-1592	2.50	63.5	.573	14.6	4.9	.86	1.8	45	8.7	39	.73	18.5	0.057	1.4	12.8	SST	CG	N
0.687	17.45	11687	2.50	63.5	.569	14.5	8.3	1.4	1.3	33	11	48	.62	15.7	0.059	1.5	10.5	SPR	CG	Z
0.687	17.45	12022	2.50	63.5	.559	14.2	9.1	1.6	1.5	39	14	61	.83	21.1	0.064	1.6	13.0	SPR	CG	Z
0.687	17.45	2739	2.50	63.5	.417	10.6	270	47	.38	9.7	103	458	1.69	42.9	0.135	3.4	12.5	SPR	CG	Z
0.687	17.45	S-3250	2.53	64.3	.571	14.5	3.4	.60	1.4	36	4.9	22	1.10	28.0	0.058	1.5	19.0	SST	CG	N
0.687	17.45	B17-165	2.53	64.3	.543	13.8	12	2.1	1.4	35	16	72	1.15	29	0.072	1.8	16.0	HD	CG	N
0.687	17.45	10654	2.59	65.9	.569	14.5	4.5	.78	1.6	42	7.3	33	.94	24.0	0.059	1.5	16.0	SST	CG	N
0.687	17.45	2998	2.66	67.5	.623	15.8	.44	.08	2.2	55	.95	4.2	.49	12.4	0.032	0.8	14.3	MW	C	Z
0.687	17.45	12282	2.69	68.2	.603	15.3	2.8	.49	1.5	39	4.2	19	.38	9.6	0.042	1.1	8.00	SPR	C	Z
0.687	17.45	3674	2.69	68.2	.495	12.6	46	8.1	.89	23	41	183	1.42	36.0	0.096	2.4	14.8	SPR	CG	Z
0.687	17.45	10556	2.75	69.9	.601	15.3	1.9	.34	2.3	57	4.4	19	.50	12.6	0.043	1.1	11.5	SPR	CG	Z
0.687	17.45	DD-86	2.75	69.9	.547	13.9	11	1.9	1.5	37	16	71	.98	24.9	0.070	1.8	14.0	SST	CG	N
0.687	17.45	12221	2.78	70.6	.515	13.1	40	7.0	.77	20	31	138	.95	24.0	0.086	2.2	11.0	SPR	CG	Z
0.687	17.45	12416	2.91	73.8	.529	13.4	26	4.6	.93	23	24	108	.99	25.1	0.079	2.0	11.5	SPR	C	N
0.687	17.45	4375	2.97	75.4	.505	12.8	33	5.8	1.1	27	35	157	1.46	37.0	0.091	2.3	16.0	SPR	CG	Z
0.687	17.45	18	3.00	76.2	.593	15.1	3.0	.52	2.0	50	5.9	26	.56	14.3	0.047	1.2	11.0	HD	C	Z
0.687	17.45	3353	3.00	76.2	.543	13.8	12	2.2	1.5	38	18	82	1.19	30.2	0.072	1.8	15.5	HD	C	Z
0.687	17.45	12023	3.25	82.6	.555	14.1	8.4	1.5	1.8	45	15	67	1.02	26.0	0.066	1.7	15.5	SPR	CG	Z
0.687	17.45	3206	3.31	84.1	.613	15.6	.70	.12	2.7	68	1.9	8.4	.63	16.0	0.037	0.9	16.0	SPR	C	Z
0.687	17.45	3089	3.31	84.1	.593	15.1	1.8	.32	2.5	63	4.4	20	.84	21.3	0.047	1.2	17.0	SPR	C	Z
0.687	17.45	11416	3.38	85.7	.605	15.4	1.7	.30	2.3	58	3.9	18	.48	12.2	0.041	1.0	10.8	HD	C	Z
0.687	17.45	506	3.63	92.1	.543	13.8	10	1.8	1.8	45	18	82	1.37	34.7	0.072	1.8	18.0	HD	C	Z
0.687	17.45	35	4.00	101.6	.477	12.1	42	7.3	1.3	33	53	237	2.44	62.0	0.105	2.7	23.3	HD	CG	Z
0.687	17.45	12187	4.41	111.9	.527	13.4	16	2.9	1.5	39	25	112	1.44	36.6	0.080	2.0	18.0	SPR	CG	Z
0.687	17.45	3925	4.50	114.3	.577	14.7	4.7	.83	1.9	47	8.8	39	.77	19.6	0.055	1.4	13.0	SPR	C	Z
0.687	17.45	11529	4.63	117.5	.571	14.5	3.9	.68	2.6	67	10	46	1.15	29.1	0.058	1.5	18.8	SPR	CG	Z
0.687	17.45	10707	4.63	117.5	.543	13.8	7.2	1.3	2.6	65	18	82	1.80	45.7	0.072	1.8	25.0	SPR	CG	Z
0.687	17.45	11821	5.25	133.4	.507	12.9	15	2.6	2.3	59	34	152	2.88	73.2	0.090	2.3	32.0	SPR	CG	Z
0.687	17.45	358	5.75	146.1	.543	13.8	6.4	1.1	2.9	73	18	82	2.07	52.6	0.072	1.8	27.8	HD	C	Z
0.687	17.45	364	6.00	152.4	.543	13.8	6.2	1.1	3.0	76	18	82	2.16	54.9	0.072	1.8	29.0	HD	C	Z
0.687	17.45	2836	6.56	166.7	.537	13.6	6.0	1.1	3.9	100	24	105	2.63	66.7	0.075	1.9	35.0	MW	CG	GI
0.687	17.45	3961	9.50	241.3	.543	13.8	4.4	.78	4.2	106	18	82	2.92	74.1	0.072	1.8	39.5	SPR	C	Z
0.687	17.45	12592	12.1	308.0	.425	10.8	38	6.7	2.5	62	95	421	8.65	219.6	0.131	3.3	66.0	SPR	CG	Z
0.687	17.45	3384	16.0	406.4	.563	14.3	1.6	.28	7.7	196	13	56	3.50	89.0	0.062	1.6	55.5	HD	C	Z
0.687	17.45	512	16.0	406.4	.563	14.3	1.3	.23	9.5	241	13	56	4.28	108.7	0.062	1.6	68.0	HD	C	Z
0.690	17.53	71925	.69	17.5	.588	14.9	107	19	.09	2.3	9.7	43	.12	3.1	0.051	1.3	2.38	MW	CG	N
0.690	17.53	71925S	.69	17.5	.588	14.9	91	16	.07	1.8	6.6	29	.12	3.1	0.051	1.3	2.38	SST	CG	N
0.703	17.86	JJ-55	.50	12.7	.635	16.1	4.5	.78	.36	9.0	1.6	7.1	.14	3.7	0.034	0.9	3.25	SST	C	N
0.703	17.86	Q-53	.50	12.7	.635	16.1	2.5	.43	.32	8.2	.80	3.5	.18	4.5	0.034	0.9	4.25	SST	C	N
0.703	17.86	S-489	.50	12.7	.621	15.8	4.1	.71	.25	6.5	1.0	4.6	.25	6.2	0.041	1.0	5.00	SST	C	N
0.703	17.86	K-12	.50	12.7	.503	12.8	656	115	.07	1.8	45	202	.30	7.6	0.100	2.5	3.00	SPR	CG	N
0.703	17.86	MM-41	.53	13.5	.603	15.3	19	3.3	.32	8.1	6.1	27	.18	4.4	0.050	1.3	3.50	SST	CG	N
0.703	17.86	S-795	.59	15.1	.609	15.5	11	1.9	.41	10	4.4	19	.19	4.8	0.047	1.2	4.00	SST	CG	N
0.703	17.86	4144	.63	15.9	.605	15.4	9.9	1.7	.33	8.4	3.3	15	.29	7.5	0.049	1.2	5.00	SPR	C	Z
0.703	17.86	I-62	.63	15.9	.595	15.1	19	3.4	.39	10	7.7	34	.22	5.5	0.054	1.4	4.00	SST	CG	N
0.703	17.86	00-68	.66	16.7	.443	11.3	1091	191	.08	2.1	91	404	.52	13.2	0.130	3.3	4.00	SPR	CG	Z
0.703	17.86	QQ-42	.69	17.4	.643	16.3	.95	.17	.48	12	.46	2.0	.21	5.3	0.030	0.8	6.00	MW	C	Z
0.703	17.86	Q-64	.69	17.4	.621	15.8	5.0	.87	.46	12	2.3	10	.23	5.7	0.041	1.0	4.50	SST	C	N
0.703	17.86	PP-79	.69	17.4	.559	14.2	53	9.4	.32	8.0	17	75	.32	8.2	0.072	1.8	4.50	SST	CG	N
0.703	17.86	3846	.75	19.1	.645	16.4	.83	.15	.55	14	.45	2.0	.20	5.2	0.029	0.7	6.00	MW	C	Z
0.703	17.86	4224	.75	19.1	.623	15.8	4.2	.74	.55	14	2.3	10	.20	5.1	0.040	1.0	5.00	SPR	CG	Z
0.703	17.86	3880	.75	19.1	.579	14.7	40	7.1	.30	7.7	12	54	.31							




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.703	17.86	2573	1.19	30.2	.639	16.2	1.2	.22	.96	24	1.2	5.3	.22	5.7	0.032	0.8	6.00	HD	C	Z
0.703	17.86	11878	1.19	30.2	.601	15.3	6.2	1.1	.83	21	5.2	23	.36	9.1	0.051	1.3	7.00	SST	CG	N
0.703	17.86	11293	1.19	30.2	.533	13.5	79	14	.37	9.4	29	131	.51	13.0	0.085	2.2	6.00	SPR	CG	Z
0.703	17.86	3951	1.25	31.8	.613	15.6	6.9	1.2	.74	19	5.1	23	.23	5.7	0.045	1.1	5.00	SPR	CG	Z
0.703	17.86	AA-69	1.25	31.8	.543	13.8	62	11	.37	9.5	23	103	.44	11.2	0.080	2.0	5.50	SST	CG	N
0.703	17.86	2676	1.25	31.8	.517	13.1	118	21	.43	11	51	229	.65	16.5	0.093	2.4	6.00	MW	C	Z
0.703	17.86	B11-66	1.25	31.8	.453	11.5	428	75	.20	5.0	84	372	.78	19.8	0.125	3.2	6.25	SPR	CG	Z
0.703	17.86	11943	1.28	32.5	.567	14.4	30	5.3	.54	14	16	72	.41	10.4	0.068	1.7	6.00	SPR	CG	Z
0.703	17.86	10139	1.31	33.3	.569	14.5	28	4.9	.55	14	15	68	.47	11.9	0.067	1.7	6.00	SPR	C	Z
0.703	17.86	10920	1.31	33.3	.513	13.0	83	15	.47	12	39	174	.78	19.9	0.095	2.4	8.25	SPR	CG	Z
0.703	17.86	3164	1.34	34.1	.575	14.6	15	2.7	.77	19	12	53	.58	14.6	0.064	1.6	8.00	SPR	C	Z
0.703	17.86	S-1680	1.41	35.7	.623	15.8	2.6	.46	1.1	28	2.9	13	.29	7.4	0.040	1.0	6.25	SST	C	N
0.703	17.86	10631	1.41	35.7	.619	15.7	2.7	.48	1.1	28	3.1	14	.29	7.5	0.042	1.1	7.00	SST	CG	N
0.703	17.86	11378	1.41	35.7	.559	14.2	24	4.2	.71	18	17	75	.56	14.2	0.072	1.8	7.75	SST	CG	N
0.703	17.86	3517	1.44	36.5	.559	14.2	24	4.1	.76	19	18	80	.61	15.5	0.072	1.8	8.50	HD	CG	Z
0.703	17.86	AA-76	1.44	36.5	.483	12.3	168	29	.34	8.7	58	258	.88	22.4	0.110	2.8	8.00	SPR	CG	N
0.703	17.86	A10-67	1.50	38.1	.631	16.0	1.8	.32	1.2	32	2.3	10	.25	6.4	0.036	0.9	6.00	SST	C	N
0.703	17.86	A15-62	1.50	38.1	.617	15.7	4.7	.82	.89	23	4.2	18	.23	5.7	0.043	1.1	5.25	SST	CG	N
0.703	17.86	11675	1.50	38.1	.583	14.8	14	2.5	.79	20	11	49	.42	10.7	0.060	1.5	7.00	SPR	CG	GI
0.703	17.86	S-1289	1.50	38.1	.579	14.7	16	2.7	.74	19	12	51	.40	10.2	0.062	1.6	6.50	SST	CG	N
0.703	17.86	B12-60	1.50	38.1	.571	14.5	22	3.9	.66	17	15	66	.51	13.0	0.066	1.7	6.75	SPR	C	Z
0.703	17.86	S-1309	1.50	38.1	.569	14.5	20	3.4	.74	19	14	64	.47	11.9	0.067	1.7	7.00	SST	CG	N
0.703	17.86	12141	1.50	38.1	.569	14.5	23	3.9	.68	17	15	68	.47	11.9	0.067	1.7	7.00	SPR	CG	Z
0.703	17.86	3581	1.50	38.1	.559	14.2	29	5.1	.86	22	25	112	.52	13.3	0.072	1.8	7.25	MW	CG	Z
0.703	17.86	GG-100	1.50	38.1	.553	14.0	17	2.9	.45	11	7.5	33	1.05	26.7	0.075	1.9	13.0	SPR	C	GI
0.703	17.86	1711	1.50	38.1	.521	13.2	123	22	.28	7.1	34	153	.50	12.7	0.091	2.3	5.50	SPR	CG	Z
0.703	17.86	3559	1.50	38.1	.507	12.9	92	16	.65	17	60	266	.83	21.2	0.098	2.5	8.50	MW	CG	Z
0.703	17.86	3813	1.63	41.3	.519	13.2	56	9.9	.63	16	36	158	.92	23.4	0.092	2.3	10.0	SPR	CG	Z
0.703	17.86	S-1000	1.66	42.1	.641	16.3	67	12	1.4	36	96	4.2	.24	6.1	0.031	0.8	7.75	SST	CG	N
0.703	17.86	S-251	1.75	44.5	.519	13.2	49	8.6	.67	17	33	147	.92	23.4	0.092	2.3	10.0	SST	CG	N
0.703	17.86	S-280	1.78	45.2	.521	13.2	48	8.3	.67	17	32	142	.91	23.1	0.091	2.3	10.0	SST	CG	N
0.703	17.86	4263	1.81	46.0	.579	14.7	10	1.8	1.1	29	11	51	.68	17.3	0.062	1.6	10.0	SPR	C	Z
0.703	17.86	12501	1.86	47.2	.543	13.8	36	6.3	.68	17	25	110	.78	19.8	0.080	2.0	8.75	SPR	C	N
0.703	17.86	12557	1.91	48.4	.545	13.8	14	2.5	.39	9.8	5.5	24	1.52	38.6	0.079	2.0	18.3	MW	C	N
0.703	17.86	4348	1.94	49.2	.521	13.2	49	8.6	.70	18	34	153	.98	24.8	0.091	2.3	10.8	SPR	CG	Z
0.703	17.86	4373	1.94	49.2	.521	13.2	51	8.9	.68	17	34	153	.96	24.3	0.091	2.3	10.5	SPR	CG	Z
0.703	17.86	10573	1.97	50.0	.573	14.6	12	2.1	1.1	28	13	59	.60	15.3	0.065	1.7	9.25	SST	CG	N
0.703	17.86	NN-96	2.00	50.8	.503	12.8	105	18	.43	11	45	202	.83	21.0	0.100	2.5	8.25	SPR	CG	Z
0.703	17.86	3462	2.13	54.0	.543	13.8	35	6.1	.71	18	25	110	.80	20.3	0.080	2.0	9.00	HD	C	Z
0.703	17.86	3422	2.19	55.6	.463	11.8	201	35	.37	9.4	74	331	1.26	32.0	0.120	3.0	9.50	SPR	C	Z
0.703	17.86	3672	2.22	56.4	.557	14.1	18	3.2	1.0	26	19	84	.80	20.4	0.073	1.9	11.0	SPR	CG	Z
0.703	17.86	S-1495	2.38	60.3	.579	14.7	5.8	1.0	1.5	38	8.8	39	.87	22.0	0.062	1.6	14.0	SST	CG	N
0.703	17.86	12335	2.53	64.3	.583	14.8	7.0	1.2	1.6	40	11	49	.78	19.8	0.060	1.5	12.0	SPR	C	Z
0.703	17.86	10415	2.56	65.1	.477	12.1	114	20	.55	14	63	278	1.36	34.4	0.113	2.9	12.0	SPR	CG	Z
0.703	17.86	12274	2.69	68.2	.577	14.7	7.9	1.4	1.6	42	13	57	.82	20.8	0.063	1.6	13.0	SPR	CG	Z
0.703	17.86	3063	2.72	69.0	.513	13.0	41	7.2	.96	24	39	174	1.40	35.6	0.095	2.4	14.8	SPR	CG	Z
0.703	17.86	GG-43	2.75	69.9	.643	16.3	34	.06	2.4	61	.81	3.6	.36	9.1	0.030	0.8	12.0	SST	CG	N
0.703	17.86	12039	2.84	72.2	.543	13.8	22	3.9	1.1	28	25	110	1.04	26.4	0.080	2.0	13.0	SPR	CG	Z
0.703	17.86	10523	3.06	77.8	.583	14.8	5.3	.93	2.1	53	11	49	.92	23.2	0.060	1.5	15.3	SPR	CG	GI
0.703	17.86	S-1200	3.38	85.7	.559	14.2	7.9	1.4	2.0	51	16	70	1.37	34.7	0.072	1.8	19.0	SST	CG	N
0.703	17.86	11274	3.50	88.9	.521	13.2	36	6.3	.96	24	34	153	1.27	32.4	0.091	2.3	14.0	SPR	CG	Z
0.703	17.86	11273	3.50	88.9	.507	12.9	33	5.8	1.3	33	43	190	1.96	49.8	0.098	2.5	20.0	SPR	CG	Z
0.703	17.86	11344	3.50	88.9	.407	10.3	336	59	.39	9.9	131	582	2.07	52.6	0.148	3.8	14.0	SPR	CG	Z
0.703	17.86	11725	4.13	104.8	.613	15.6	2.3	.40	2.2	56	5.1	23	.50	12.6	0.045	1.1	11.0	SPR	CG	GI
0.703	17.86	3052	4.13	104.8	.579	14.7	5.0	.88	2.4	62	12	54	1.12	28.3	0.062	1.6	18.0	SPR	CG	Z
0.703	17.86	12450	4.13	104.8	.493	12.5	50	8.7	1.1	27	52	233	1.94	49.3	0.105	2.7	18.5	SPR	CG	Z
0.703	17.86	10446	4.25	108.0	.463	11.8	66	12	1.1	29	74	331	2.97	75.4	0.120	3.0	24.8	SPR	CG	Z
0.703	17.86	12283	4.41	111.9	.553	14.0	9.2	1.6</												



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.718	18.24	11458	.75	19.1	.574	14.6	51	8.9	.33	8.3	17	74	.40	10.1	0.072	1.8	4.50	SST	C	N
0.718	18.24	A9-38	.81	20.6	.634	16.1	6.4	1.1	.59	15	3.8	17	.21	5.3	0.042	1.1	4.00	SST	C	N
0.718	18.24	A14-47	.81	20.6	.478	12.1	612	107	.11	2.8	67	296	.48	12.2	0.120	3.0	4.00	SST	CG	N
0.718	18.24	12729	.87	22.0	.638	16.2	4.1	.72	.67	17	2.8	12	.20	5.0	0.040	1.0	4.88	MW	CG	BO
0.718	18.24	S-1364	.88	22.2	.594	15.1	24	4.2	.47	12	11	50	.29	7.5	0.062	1.6	4.75	SST	CG	N
0.718	18.24	10233	.88	22.2	.574	14.6	25	4.4	.32	8.1	7.9	35	.56	14.2	0.072	1.8	7.75	SPR	CG	Z
0.718	18.24	S-1082	1.00	25.4	.638	16.2	2.9	.51	.74	19	2.2	9.7	.26	6.6	0.040	1.0	5.50	SST	C	N
0.718	18.24	A12-41	1.00	25.4	.628	16.0	6.4	1.1	.73	19	4.7	21	.27	6.9	0.045	1.1	5.00	MW	C	Z
0.718	18.24	RR-33	1.00	25.4	.618	15.7	7.5	1.3	.65	17	4.9	22	.35	8.9	0.050	1.3	6.00	SPR	C	Z
0.718	18.24	S-878	1.00	25.4	.610	15.5	11	2.0	.67	17	7.5	33	.28	7.2	0.054	1.4	5.25	SST	CG	N
0.718	18.24	3973	1.00	25.4	.574	14.6	48	8.4	.37	9.4	18	79	.43	11.0	0.072	1.8	5.00	SPR	C	Z
0.718	18.24	CC-80	1.00	25.4	.546	13.9	98	17	.28	7.2	28	124	.41	10.4	0.086	2.2	4.75	SST	CG	N
0.718	18.24	S-1260	1.03	26.2	.636	16.2	3.3	.57	.81	20	2.6	12	.23	5.7	0.041	1.0	5.50	SST	CG	N
0.718	18.24	S-3077	1.13	28.6	.614	15.6	7.7	1.4	.81	21	6.3	28	.31	7.9	0.052	1.3	6.00	SST	CG	N
0.718	18.24	10907	1.16	29.4	.628	16.0	3.4	.60	.84	21	2.9	13	.32	8.0	0.045	1.1	7.00	SST	CG	N
0.718	18.24	S-246	1.22	31.0	.624	15.8	5.0	.88	.89	23	4.5	20	.33	8.4	0.047	1.2	6.00	SST	C	N
0.718	18.24	S-430	1.22	31.0	.608	15.4	6.9	1.2	.80	20	5.5	25	.42	10.7	0.055	1.4	7.67	SST	CG	N
0.718	18.24	QQ-44	1.25	31.8	.534	13.6	56	9.8	.38	9.6	21	94	.87	22.2	0.092	2.3	9.50	SPR	CG	Z
0.718	18.24	S-1034	1.31	33.3	.634	16.1	4.2	.73	.90	23	3.8	17	.25	6.4	0.042	1.1	5.00	SST	C	N
0.718	18.24	3792	1.31	33.3	.614	15.6	7.9	1.4	.90	23	7.1	32	.34	8.6	0.052	1.3	6.50	SPR	CG	GI
0.718	18.24	B11-4	1.31	33.3	.594	15.1	11	1.9	.75	19	8.1	36	.56	14.2	0.062	1.6	9.00	SPR	CG	N
0.718	18.24	M-145	1.31	33.3	.572	14.5	43	7.6	.42	11	18	82	.47	12.1	0.073	1.9	5.50	SPR	C	GI
0.718	18.24	S-69	1.34	34.1	.610	15.5	14	2.4	.55	14	7.5	33	.25	6.4	0.054	1.4	4.67	SST	CG	N
0.718	18.24	B10-56	1.38	34.9	.618	15.7	7.5	1.3	.84	21	6.3	28	.30	7.6	0.050	1.3	6.00	SPR	CG	N
0.718	18.24	KK-56	1.38	34.9	.578	14.7	23	4.0	.71	18	16	73	.53	13.3	0.070	1.8	7.50	SPR	CG	N
0.718	18.24	3993	1.38	34.9	.478	12.1	199	35	.30	7.5	59	261	1.08	27.4	0.120	3.0	9.00	SPR	CG	Z
0.718	18.24	Q-51	1.41	35.7	.568	14.4	31	5.4	.64	16	20	89	.56	14.3	0.075	1.9	7.50	SPR	CG	N
0.718	18.24	B9-62	1.50	38.1	.622	15.8	6.3	1.1	.95	24	6.0	27	.34	8.5	0.048	1.2	6.00	SPR	C	N
0.718	18.24	S-48	1.50	38.1	.594	15.1	11	1.9	1.0	26	11	49	.50	12.6	0.062	1.6	8.00	SST	CG	N
0.718	18.24	S-3252	1.50	38.1	.446	11.3	443	77	.21	5.2	91	406	.95	24.2	0.136	3.5	7.00	SST	CG	N
0.718	18.24	B6-54	1.59	40.5	.654	16.6	.93	.16	1.4	35	1.3	5.7	.22	5.7	0.032	0.8	7.00	SPR	CG	Z
0.718	18.24	10565	1.59	40.5	.488	12.4	118	21	.24	6.1	28	127	1.35	34.3	0.115	2.9	11.8	SPR	CG	Z
0.718	18.24	S-1431	1.63	41.3	.636	16.2	2.4	.42	1.3	34	3.2	14	.28	7.0	0.041	1.0	6.75	SST	CG	N
0.718	18.24	11252	1.63	41.3	.528	13.4	59	10	.65	16	38	171	.88	22.3	0.095	2.4	9.25	SPR	CG	N
0.718	18.24	3829	1.63	41.3	.508	12.9	101	18	.51	13	51	228	1.00	25.3	0.105	2.7	9.50	SPR	CG	Z
0.718	18.24	11612	1.63	41.3	.458	11.6	274	48	.25	6.5	70	311	1.37	34.8	0.130	3.3	9.50	SPR	CG	Z
0.718	18.24	10633	1.69	42.8	.622	15.8	3.6	.63	1.2	31	4.4	19	.48	12.2	0.048	1.2	9.00	SPR	C	Z
0.718	18.24	10070	1.69	42.8	.394	10.0	1047	183	.15	3.9	161	718	1.22	30.9	0.162	4.1	7.50	SPR	CG	Z
0.718	18.24	S-370	1.75	44.5	.654	16.6	.90	.16	1.5	38	1.4	6.1	.24	6.1	0.032	0.8	6.50	SST	C	N
0.718	18.24	S-285	1.75	44.5	.636	16.2	1.1	.20	1.3	32	1.4	6.4	.49	12.5	0.041	1.0	12.0	SST	CG	N
0.718	18.24	S-849	1.81	46.0	.574	14.6	12	2.2	.95	24	12	53	.86	21.9	0.072	1.8	12.0	SST	CG	N
0.718	18.24	10209	1.81	46.0	.354	9.0	1517	266	.14	3.5	212	941	1.59	40.5	0.182	4.6	8.75	SPR	CG	Z
0.718	18.24	11588	1.88	47.6	.598	15.2	10	1.8	1.1	28	11	48	.57	14.5	0.060	1.5	8.50	SPR	CG	Z
0.718	18.24	2946	1.88	47.6	.584	14.8	17	3.1	.86	22	15	67	.60	15.3	0.067	1.7	8.00	SPR	C	Z
0.718	18.24	11756	1.91	48.4	.524	13.3	71	12	.58	15	41	181	.92	23.4	0.097	2.5	9.50	SPR	CG	Z
0.718	18.24	10599	1.94	49.2	.530	13.5	54	9.5	.68	17	37	165	.99	25.1	0.094	2.4	10.5	SPR	CG	Z
0.718	18.24	YY-33	2.00	50.8	.628	16.0	2.4	.42	1.6	39	3.7	17	.45	11.4	0.045	1.1	9.00	SST	C	N
0.718	18.24	S-1440	2.00	50.8	.584	14.8	13	2.3	1.1	28	14	63	.60	15.3	0.067	1.7	9.00	SST	CG	N
0.718	18.24	10257	2.00	50.8	.536	13.6	53	9.3	.63	16	34	150	.96	24.3	0.091	2.3	9.50	SPR	C	Z
0.718	18.24	A15-53	2.00	50.8	.528	13.4	57	10	.62	16	36	158	.90	22.9	0.095	2.4	9.50	SST	CG	N
0.718	18.24	A13-33	2.03	51.6	.582	14.8	15	2.6	1.0	26	15	66	.60	15.1	0.068	1.7	8.75	SST	CG	N
0.718	18.24	2778	2.06	52.4	.568	14.4	25	4.4	1.1	28	28	124	.73	18.6	0.075	1.9	8.75	MW	C	Z
0.718	18.24	10867	2.13	54.0	.594	15.1	13	2.2	.96	24	12	53	.50	12.6	0.062	1.6	8.00	SPR	CG	GI
0.718	18.24	4367	2.13	54.0	.584	14.8	11	1.9	1.4	34	15	67	.77	19.6	0.067	1.7	11.5	SPR	CG	Z
0.718	18.24	B9-56	2.13	54.0	.556	14.1	27	4.8	.86	22	23	104	.79	20.1	0.081	2.1	9.75	SST	CG	N
0.718	18.24	2651	2.19	55.6	.488	12.4	104	18	.62	16	65	287	1.50	38.0	0.115	2.9	13.0	SPR	CG	Z
0.718	18.24	S-1630	2.22	56.4	.636	16.2	1.5	.27	1.8	46	2.8	13	.39	9.9	0.041	1.				



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./in.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.719	18.26	U-84	.61	15.5	.637	16.2	2.5	.44	.34	8.7	.86	3.8	.27	6.8	0.041	1.0	6.50	SST		
0.720	18.29	71926	.63	16.0	.610	15.5	31	5.4	.38	9.7	12	52	.19	4.9	0.055	1.4	3.50	MW	CG	N
0.720	18.29	71926S	.63	16.0	.610	15.5	26	4.6	.30	7.7	7.9	35	.19	4.9	0.055	1.4	3.50	SST	CG	N
0.720	18.29	71951	.63	16.0	.594	15.1	47	8.2	.37	9.5	17	78	.24	6.0	0.063	1.6	3.75	MW	CG	N
0.720	18.29	71951S	.63	16.0	.594	15.1	40	7.0	.30	7.5	12	53	.24	6.0	0.063	1.6	3.75	SST	CG	N
0.720	18.29	71927	.75	19.1	.610	15.5	23	4.0	.51	13	12	52	.22	5.6	0.055	1.4	4.00	MW	CG	N
0.720	18.29	71927S	.75	19.1	.610	15.5	20	3.4	.40	10	7.9	35	.22	5.6	0.055	1.4	4.00	SST	CG	N
0.720	18.29	71938	.75	19.1	.602	15.3	33	5.8	.44	11	14	64	.23	5.8	0.059	1.5	3.88	MW	CG	N
0.720	18.29	71938S	.75	19.1	.602	15.3	28	4.9	.35	8.8	9.7	43	.23	5.8	0.059	1.5	3.88	SST	CG	N
0.720	18.29	71952	.75	19.1	.594	15.1	33	5.8	.47	12	16	70	.28	7.0	0.063	1.6	4.38	MW	CG	N
0.720	18.29	71952S	.75	19.1	.594	15.1	28	4.9	.42	11	12	53	.28	7.0	0.063	1.6	4.38	SST	CG	N
0.720	18.29	71963	.75	19.1	.590	15.0	44	7.6	.44	11	19	85	.27	6.8	0.065	1.7	4.13	MW	CG	N
0.720	18.29	71963S	.75	19.1	.590	15.0	37	6.5	.35	8.9	13	58	.27	6.8	0.065	1.7	4.13	SST	CG	N
0.720	18.29	71976	.75	19.1	.586	14.9	50	8.8	.42	11	21	93	.28	7.0	0.067	1.7	4.13	MW	CG	N
0.720	18.29	71976S	.75	19.1	.586	14.9	43	7.4	.33	8.5	14	63	.28	7.0	0.067	1.7	4.13	SST	CG	N
0.720	18.29	71991	.75	19.1	.584	14.8	50	8.7	.44	11	22	97	.29	7.3	0.068	1.7	4.25	MW	CG	N
0.720	18.29	71991S	.75	19.1	.584	14.8	42	7.4	.35	8.9	15	66	.29	7.3	0.068	1.7	4.25	SST	CG	N
0.720	18.29	72014	.75	19.1	.576	14.6	67	12	.37	9.3	25	110	.30	7.5	0.072	1.8	4.13	MW	CG	N
0.720	18.29	72014S	.75	19.1	.576	14.6	57	10	.29	7.4	17	74	.30	7.5	0.072	1.8	4.13	SST	CG	N
0.720	18.29	72029	.75	19.1	.560	14.2	92	16	.37	9.3	34	150	.36	9.1	0.080	2.0	4.50	MW	CG	N
0.720	18.29	72029S	.75	19.1	.560	14.2	78	14	.29	7.3	23	100	.36	9.1	0.080	2.0	4.50	SST	CG	N
0.720	18.29	72057	.75	19.1	.558	14.2	104	18	.34	8.6	35	155	.34	8.7	0.081	2.1	4.25	MW	CG	N
0.720	18.29	72057S	.75	19.1	.558	14.2	88	15	.27	6.8	23	104	.34	8.7	0.081	2.1	4.25	SST	CG	N
0.720	18.29	72070	.75	19.1	.550	14.0	139	24	.29	7.3	40	179	.35	8.9	0.085	2.2	4.13	MW	CG	N
0.720	18.29	72070S	.75	19.1	.550	14.0	118	21	.23	5.8	27	120	.35	8.9	0.085	2.2	4.13	SST	CG	N
0.720	18.29	72097	.75	19.1	.528	13.4	239	42	.23	5.9	55	245	.40	10.1	0.096	2.4	4.13	MW	CG	N
0.720	18.29	72097S	.75	19.1	.528	13.4	203	36	.18	4.6	37	163	.40	10.1	0.096	2.4	4.13	SST	CG	N
0.720	18.29	72110	.75	19.1	.510	13.0	355	62	.20	5.1	72	318	.43	11.0	0.105	2.7	4.13	MW	CG	N
0.720	18.29	72110S	.75	19.1	.510	13.0	301	53	.16	4.0	47	211	.43	11.0	0.105	2.7	4.13	SST	CG	N
0.720	18.29	72123	.75	19.1	.496	12.6	469	82	.18	4.5	83	371	.46	11.7	0.112	2.8	4.13	MW	CG	N
0.720	18.29	72123S	.75	19.1	.496	12.6	398	70	.14	3.5	54	242	.46	11.7	0.112	2.8	4.13	SST	CG	N
0.720	18.29	71928	.88	22.4	.610	15.5	20	3.5	.58	15	12	52	.23	5.9	0.055	1.4	4.25	MW	CG	N
0.720	18.29	71928S	.88	22.4	.610	15.5	17	3.0	.46	12	7.9	35	.23	5.9	0.055	1.4	4.25	SST	CG	N
0.720	18.29	71939	.88	22.4	.602	15.3	27	4.8	.53	13	14	64	.25	6.4	0.059	1.5	4.25	MW	CG	N
0.720	18.29	71939S	.88	22.4	.602	15.3	23	4.1	.42	11	9.7	43	.25	6.4	0.059	1.5	4.25	SST	CG	N
0.720	18.29	71953	.88	22.4	.594	15.1	28	4.9	.57	15	16	71	.31	7.8	0.063	1.6	4.88	MW	CG	N
0.720	18.29	71953S	.88	22.4	.594	15.1	24	4.2	.50	13	12	53	.31	7.8	0.063	1.6	4.88	SST	CG	N
0.720	18.29	71964	.88	22.4	.590	15.0	37	6.4	.52	13	19	85	.29	7.4	0.065	1.7	4.50	MW	CG	N
0.720	18.29	71964S	.88	22.4	.590	15.0	31	5.4	.42	11	13	58	.29	7.4	0.065	1.7	4.50	SST	CG	N
0.720	18.29	71977	.88	22.4	.586	14.9	40	7.0	.52	13	21	93	.31	7.9	0.067	1.7	4.63	MW	CG	N
0.720	18.29	71977S	.88	22.4	.586	14.9	34	6.0	.42	11	14	63	.31	7.9	0.067	1.7	4.63	SST	CG	N
0.720	18.29	71993	.88	22.4	.584	14.8	41	7.2	.53	13	22	97	.31	8.0	0.068	1.7	4.63	MW	CG	N
0.720	18.29	71993S	.88	22.4	.584	14.8	35	6.2	.42	11	15	66	.31	8.0	0.068	1.7	4.63	SST	CG	N
0.720	18.29	72015	.88	22.4	.576	14.6	48	8.4	.51	13	25	110	.36	9.1	0.072	1.8	5.00	MW	CG	N
0.720	18.29	72015S	.88	22.4	.576	14.6	41	7.1	.41	10	17	74	.36	9.1	0.072	1.8	5.00	SST	CG	N
0.720	18.29	72031	.88	22.4	.560	14.2	76	13	.44	11	34	150	.40	10.2	0.080	2.0	5.00	MW	CG	N
0.720	18.29	72031S	.88	22.4	.560	14.2	65	11	.35	8.9	23	100	.40	10.2	0.080	2.0	5.00	SST	CG	N
0.720	18.29	72058	.88	22.4	.558	14.2	82	14	.42	11	35	155	.39	10.0	0.081	2.1	4.88	MW	CG	N
0.720	18.29	72058S	.88	22.4	.558	14.2	70	12	.33	8.5	23	104	.39	10.0	0.081	2.1	4.88	SST	CG	N
0.720	18.29	72071	.88	22.4	.550	14.0	114	20	.35	9.0	40	179	.39	10.0	0.085	2.2	4.63	MW	CG	N
0.720	18.29	72071S	.88	22.4	.550	14.0	97	17	.28	7.1	27	120	.39	10.0	0.085	2.2	4.63	SST	CG	N
0.720	18.29	72098	.88	22.4	.528	13.4	194	34	.28	7.2	55	245	.44	11.3	0.096	2.4	4.63	MW	CG	N
0.720	18.29	72098S	.88	22.4	.528	13.4	165	29	.22	5.6	37	163	.44	11.3	0.096	2.4	4.63	SST	CG	N
0.720	18.29	72111	.88	22.4	.510	13.0	286	50	.25	6.4	72	318	.49	12.3	0.105	2.7	4.63	MW	CG	N
0.720	18.29	72111S	.88	22.4	.510	13.0	243	43	.20	5.0	47	211	.49	12.3	0.105	2.7	4.63	SST	CG	N
0.720	18.29	72124	.88	22.4	.496	12.6	374	66	.22	5.7	83	371	.53	13.5	0.112	2.8	4.75	MW	CG	N
0.720	18.29	72124S	.88	22.4	.496	12.6	318	56	.17	4.3	54	242	.53	13.5	0.112	2.8	4.75	SST	CG	N
0.720	18.29	71929	1.00	25.4	.610	15.5	19	3.2	.63	16	12	52	.24	6.1	0.055	1.4	4.38	MW	CG	N
0.720	18																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.720	18.29	72099S	1.00	25.4	.528	13.4	140	25	.26	6.6	37	163	.48	12.2	0.096	2.4	5.00	SST	CG	N
0.720	18.29	72112	1.00	25.4	.510	13.0	243	42	.30	7.5	72	318	.54	13.7	0.105	2.7	5.13	MW	CG	N
0.720	18.29	72112S	1.00	25.4	.510	13.0	206	36	.23	5.8	47	211	.54	13.7	0.105	2.7	5.13	SST	CG	N
0.720	18.29	72125	1.00	25.4	.496	12.6	315	55	.26	6.7	83	371	.59	14.9	0.112	2.8	5.25	MW	CG	N
0.720	18.29	72125S	1.00	25.4	.496	12.6	268	47	.20	5.2	54	242	.59	14.9	0.112	2.8	5.25	SST	CG	N
0.720	18.29	71930	1.25	31.8	.610	15.5	15	2.5	.80	20	12	52	.28	7.2	0.055	1.4	5.13	MW	CG	N
0.720	18.29	71930S	1.25	31.8	.610	15.5	12	2.2	.64	16	7.9	35	.28	7.2	0.055	1.4	5.13	SST	CG	N
0.720	18.29	71941	1.25	31.8	.602	15.3	18	3.2	.78	20	14	64	.31	7.9	0.059	1.5	5.25	MW	CG	N
0.720	18.29	71941S	1.25	31.8	.602	15.3	16	2.7	.63	16	9.7	43	.31	7.9	0.059	1.5	5.25	SST	CG	N
0.720	18.29	71955	1.25	31.8	.594	15.1	19	3.3	.86	22	16	71	.39	10.0	0.063	1.6	6.25	MW	CG	N
0.720	18.29	71955S	1.25	31.8	.594	15.1	16	2.8	.74	19	12	53	.39	10.0	0.063	1.6	6.25	SST	CG	N
0.720	18.29	71966	1.25	31.8	.590	15.0	24	4.2	.79	20	19	85	.37	9.5	0.065	1.7	5.75	MW	CG	N
0.720	18.29	71966S	1.25	31.8	.590	15.0	21	3.6	.63	16	13	58	.37	9.5	0.065	1.7	5.75	SST	CG	N
0.720	18.29	71979	1.25	31.8	.586	14.9	27	4.7	.77	20	21	93	.39	10.0	0.067	1.7	5.88	MW	CG	N
0.720	18.29	71979S	1.25	31.8	.586	14.9	23	4.0	.62	16	14	63	.39	10.0	0.067	1.7	5.88	SST	CG	N
0.720	18.29	71997	1.25	31.8	.584	14.8	28	4.8	.79	20	22	97	.41	10.4	0.068	1.7	6.00	MW	CG	N
0.720	18.29	71997S	1.25	31.8	.584	14.8	23	4.1	.63	16	15	66	.41	10.4	0.068	1.7	6.00	SST	CG	N
0.720	18.29	72017	1.25	31.8	.576	14.6	34	6.0	.73	18	25	110	.44	11.2	0.072	1.8	6.13	MW	CG	N
0.720	18.29	72017S	1.25	31.8	.576	14.6	29	5.1	.57	15	17	74	.44	11.2	0.072	1.8	6.13	SST	CG	N
0.720	18.29	72036	1.25	31.8	.560	14.2	50	8.7	.68	17	34	150	.52	13.2	0.080	2.0	6.50	MW	CG	N
0.720	18.29	72036S	1.25	31.8	.560	14.2	42	7.4	.53	14	23	100	.52	13.2	0.080	2.0	6.50	SST	CG	N
0.720	18.29	72037	1.25	31.8	.560	14.2	83	14	.41	10	34	150	.38	9.7	0.080	2.0	4.75	MW	CG	N
0.720	18.29	72037S	1.25	31.8	.560	14.2	70	12	.32	8.2	23	100	.38	9.7	0.080	2.0	4.75	SST	CG	N
0.720	18.29	72060	1.25	31.8	.558	14.2	54	9.5	.64	16	35	155	.52	13.1	0.081	2.1	6.38	MW	CG	N
0.720	18.29	72060S	1.25	31.8	.558	14.2	46	8.1	.51	13	23	104	.52	13.1	0.081	2.1	6.38	SST	CG	N
0.720	18.29	72073	1.25	31.8	.550	14.0	75	13	.54	14	40	179	.50	12.7	0.085	2.2	5.88	MW	CG	N
0.720	18.29	72073S	1.25	31.8	.550	14.0	63	11	.43	11	27	120	.50	12.7	0.085	2.2	5.88	SST	CG	N
0.720	18.29	72100	1.25	31.8	.528	13.4	126	22	.44	11	55	245	.58	14.6	0.096	2.4	6.00	MW	CG	N
0.720	18.29	72100S	1.25	31.8	.528	13.4	107	19	.34	8.7	37	163	.58	14.6	0.096	2.4	6.00	SST	CG	N
0.720	18.29	72113	1.25	31.8	.510	13.0	184	32	.39	9.9	72	318	.64	16.3	0.105	2.7	6.13	MW	CG	N
0.720	18.29	72113S	1.25	31.8	.510	13.0	157	27	.30	7.7	47	211	.64	16.3	0.105	2.7	6.13	SST	CG	N
0.720	18.29	72126	1.25	31.8	.496	12.6	238	42	.35	8.9	83	371	.70	17.8	0.112	2.8	6.25	MW	CG	N
0.720	18.29	72126S	1.25	31.8	.496	12.6	203	35	.27	6.8	54	242	.70	17.8	0.112	2.8	6.25	SST	CG	N
0.720	18.29	71931	1.50	38.1	.610	15.5	12	2.0	1.0	26	12	52	.32	8.2	0.055	1.4	5.88	MW	CG	N
0.720	18.29	71931S	1.50	38.1	.610	15.5	9.8	1.7	.81	21	7.9	35	.32	8.2	0.055	1.4	5.88	SST	CG	N
0.720	18.29	71942	1.50	38.1	.602	15.3	15	2.6	.96	24	14	64	.35	9.0	0.059	1.5	6.00	MW	CG	N
0.720	18.29	71942S	1.50	38.1	.602	15.3	13	2.2	.76	19	9.7	43	.35	9.0	0.059	1.5	6.00	SST	CG	N
0.720	18.29	71956	1.50	38.1	.594	15.1	15	2.6	1.0	26	16	69	.46	11.8	0.063	1.6	7.38	MW	CG	N
0.720	18.29	71956S	1.50	38.1	.594	15.1	13	2.2	.93	24	12	53	.46	11.8	0.063	1.6	7.38	SST	CG	N
0.720	18.29	71967	1.50	38.1	.590	15.0	20	3.5	.96	24	19	85	.43	10.9	0.065	1.7	6.63	MW	CG	N
0.720	18.29	71967S	1.50	38.1	.590	15.0	17	3.0	.77	19	13	58	.43	10.9	0.065	1.7	6.63	SST	CG	N
0.720	18.29	71980	1.50	38.1	.586	14.9	22	3.9	.95	24	21	93	.45	11.5	0.067	1.7	6.75	MW	CG	N
0.720	18.29	71980S	1.50	38.1	.586	14.9	19	3.3	.76	19	14	63	.45	11.5	0.067	1.7	6.75	SST	CG	N
0.720	18.29	71999	1.50	38.1	.584	14.8	22	3.9	.97	25	22	97	.48	12.1	0.068	1.7	7.00	MW	CG	N
0.720	18.29	71999S	1.50	38.1	.584	14.8	19	3.3	.78	20	15	66	.48	12.1	0.068	1.7	7.00	SST	CG	N
0.720	18.29	72018	1.50	38.1	.576	14.6	26	4.6	.95	24	25	110	.54	13.7	0.072	1.8	7.50	MW	CG	N
0.720	18.29	72018S	1.50	38.1	.576	14.6	22	3.9	.75	19	17	74	.54	13.7	0.072	1.8	7.50	SST	CG	N
0.720	18.29	72039	1.50	38.1	.560	14.2	41	7.1	.83	21	34	150	.60	15.2	0.080	2.0	7.50	MW	CG	N
0.720	18.29	72039S	1.50	38.1	.560	14.2	34	6.0	.66	17	23	100	.60	15.2	0.080	2.0	7.50	SST	CG	N
0.720	18.29	72040	1.50	38.1	.560	14.2	67	12	.50	13	34	150	.43	10.9	0.080	2.0	5.38	MW	CG	N
0.720	18.29	72040S	1.50	38.1	.560	14.2	57	10	.40	10	23	100	.43	10.9	0.080	2.0	5.38	SST	CG	N
0.720	18.29	72061	1.50	38.1	.558	14.2	44	7.7	.79	20	35	155	.60	15.2	0.081	2.1	7.38	MW	CG	N
0.720	18.29	72061S	1.50	38.1	.558	14.2	38	6.6	.62	16	23	104	.60	15.2	0.081	2.1	7.38	SST	CG	N
0.720	18.29	72074	1.50	38.1	.550	14.0	61	11	.66	17	40	179	.58	14.8	0.085	2.2	6.88	MW	CG	N
0.720	18.29	72074S	1.50	38.1	.550	14.0	51	9.0	.52	13	27	120	.58	14.8	0.085	2.2	6.88	SST	CG	N
0.720	18.29	72101	1.50	38.1	.528	13.4	102	18	.54	14	55	245	.66	16.8	0.096	2.4	6.88	MW	CG	N
0.720	18.29	72101S	1.50	38.1	.528	13.4	87	15	.42	11	37	163	.66	16.8	0.0					




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.720	18.29	72075S	1.75	44.5	.550	14.0	43	7.6	.62	16	27	120	.66	16.7	0.085	2.2	7.75	SST	CG	N
0.720	18.29	72084	1.75	44.5	.538	13.7	56	9.8	.84	21	47	210	.82	20.8	0.091	2.3	9.00	MW	CG	N
0.720	18.29	72084S	1.75	44.5	.538	13.7	48	8.4	.65	17	31	139	.82	20.8	0.091	2.3	9.00	SST	CG	N
0.720	18.29	72102	1.75	44.5	.528	13.4	86	15	.65	16	55	245	.76	19.2	0.096	2.4	7.88	MW	CG	N
0.720	18.29	72102S	1.75	44.5	.528	13.4	73	13	.50	13	37	163	.76	19.2	0.096	2.4	7.88	SST	CG	N
0.720	18.29	72115	1.75	44.5	.510	13.0	124	22	.58	15	72	318	.84	21.3	0.105	2.7	8.00	MW	CG	N
0.720	18.29	72115S	1.75	44.5	.510	13.0	106	19	.45	11	47	211	.84	21.3	0.105	2.7	8.00	SST	CG	N
0.720	18.29	72128	1.75	44.5	.496	12.6	160	28	.52	13	83	371	.92	23.5	0.112	2.8	8.25	MW	CG	N
0.720	18.29	72128S	1.75	44.5	.496	12.6	136	24	.40	10	54	242	.92	23.5	0.112	2.8	8.25	SST	CG	N
0.720	18.29	71933	2.00	50.8	.610	15.5	8.5	1.5	1.4	35	12	52	.40	10.1	0.055	1.4	7.25	MW	CG	N
0.720	18.29	71933S	2.00	50.8	.610	15.5	7.2	1.3	1.1	28	7.9	35	.40	10.1	0.055	1.4	7.25	SST	CG	N
0.720	18.29	71944	2.00	50.8	.602	15.3	11	1.9	1.3	33	14	64	.44	11.2	0.059	1.5	7.50	MW	CG	N
0.720	18.29	71944S	2.00	50.8	.602	15.3	9.4	1.6	1.0	26	9.7	43	.44	11.2	0.059	1.5	7.50	SST	CG	N
0.720	18.29	71958	2.00	50.8	.594	15.1	11	1.9	1.4	36	16	69	.58	14.8	0.063	1.6	9.25	MW	CG	N
0.720	18.29	71958S	2.00	50.8	.594	15.1	9.4	1.6	1.3	32	12	53	.58	14.8	0.063	1.6	9.25	SST	CG	N
0.720	18.29	71969	2.00	50.8	.590	15.0	14	2.5	1.3	34	19	85	.54	13.8	0.065	1.7	8.38	MW	CG	N
0.720	18.29	71969S	2.00	50.8	.590	15.0	12	2.1	1.1	27	13	58	.54	13.8	0.065	1.7	8.38	SST	CG	N
0.720	18.29	71982	2.00	50.8	.586	14.9	16	2.7	1.3	34	21	93	.59	14.9	0.067	1.7	8.75	MW	CG	N
0.720	18.29	71982S	2.00	50.8	.586	14.9	13	2.3	1.1	27	14	63	.59	14.9	0.067	1.7	8.75	SST	CG	N
0.720	18.29	72003	2.00	50.8	.584	14.8	16	2.9	1.3	34	22	97	.60	15.1	0.068	1.7	8.75	MW	CG	N
0.720	18.29	72003S	2.00	50.8	.584	14.8	14	2.4	1.1	27	15	66	.60	15.1	0.068	1.7	8.75	SST	CG	N
0.720	18.29	72020	2.00	50.8	.576	14.6	20	3.5	1.2	31	25	110	.66	16.7	0.072	1.8	9.13	MW	CG	N
0.720	18.29	72020S	2.00	50.8	.576	14.6	17	3.0	.97	25	17	74	.66	16.7	0.072	1.8	9.13	SST	CG	N
0.720	18.29	72044	2.00	50.8	.560	14.2	30	5.2	1.1	29	34	150	.77	19.6	0.080	2.0	9.63	MW	CG	N
0.720	18.29	72044S	2.00	50.8	.560	14.2	25	4.4	.90	23	23	100	.77	19.6	0.080	2.0	9.63	SST	CG	N
0.720	18.29	72063	2.00	50.8	.558	14.2	32	5.6	1.1	28	35	155	.76	19.3	0.081	2.1	9.38	MW	CG	N
0.720	18.29	72063S	2.00	50.8	.558	14.2	27	4.8	.86	22	23	104	.76	19.3	0.081	2.1	9.38	SST	CG	N
0.720	18.29	72076	2.00	50.8	.550	14.0	44	7.7	.91	23	40	179	.73	18.6	0.085	2.2	8.63	MW	CG	N
0.720	18.29	72076S	2.00	50.8	.550	14.0	37	6.5	.72	18	27	120	.73	18.6	0.085	2.2	8.63	SST	CG	N
0.720	18.29	72086	2.00	50.8	.538	13.7	49	8.5	.97	25	47	210	.92	23.4	0.091	2.3	10.1	MW	CG	N
0.720	18.29	72086S	2.00	50.8	.538	13.7	41	7.2	.76	19	31	139	.92	23.4	0.091	2.3	10.1	SST	CG	N
0.720	18.29	72103	2.00	50.8	.528	13.4	74	13	.75	19	55	245	.85	21.6	0.096	2.4	8.88	MW	CG	N
0.720	18.29	72103S	2.00	50.8	.528	13.4	63	11	.58	15	37	163	.85	21.6	0.096	2.4	8.88	SST	CG	N
0.720	18.29	72116	2.00	50.8	.510	13.0	107	19	.67	17	72	318	.95	24.0	0.105	2.7	9.00	MW	CG	N
0.720	18.29	72116S	2.00	50.8	.510	13.0	91	16	.52	13	47	211	.95	24.0	0.105	2.7	9.00	SST	CG	N
0.720	18.29	72129	2.00	50.8	.496	12.6	138	24	.61	15	83	371	1.04	26.3	0.112	2.8	9.25	MW	CG	N
0.720	18.29	72129S	2.00	50.8	.496	12.6	117	21	.47	12	54	242	1.04	26.3	0.112	2.8	9.25	SST	CG	N
0.720	18.29	71934	2.25	57.2	.610	15.5	7.5	1.3	1.5	39	12	52	.44	11.2	0.055	1.4	8.00	MW	CG	N
0.720	18.29	71934S	2.25	57.2	.610	15.5	6.4	1.1	1.2	31	7.9	35	.44	11.2	0.055	1.4	8.00	SST	CG	N
0.720	18.29	71945	2.25	57.2	.602	15.3	9.7	1.7	1.5	38	14	64	.49	12.4	0.059	1.5	8.25	MW	CG	N
0.720	18.29	71945S	2.25	57.2	.602	15.3	8.2	1.4	1.2	30	9.7	43	.49	12.4	0.059	1.5	8.25	SST	CG	N
0.720	18.29	71959	2.25	57.2	.594	15.1	11	1.9	1.6	40	17	78	.58	14.8	0.063	1.6	9.25	MW	CG	N
0.720	18.29	71959S	2.25	57.2	.594	15.1	9.4	1.6	1.3	32	12	53	.58	14.8	0.063	1.6	9.25	SST	CG	N
0.720	18.29	71970	2.25	57.2	.590	15.0	13	2.2	1.5	38	19	85	.60	15.3	0.065	1.7	9.25	MW	CG	N
0.720	18.29	71970S	2.25	57.2	.590	15.0	11	1.9	1.2	30	13	58	.60	15.3	0.065	1.7	9.25	SST	CG	N
0.720	18.29	71983	2.25	57.2	.586	14.9	14	2.5	1.4	37	21	93	.62	15.7	0.067	1.7	9.25	MW	CG	N
0.720	18.29	71983S	2.25	57.2	.586	14.9	12	2.2	1.2	29	14	63	.62	15.7	0.067	1.7	9.25	SST	CG	N
0.720	18.29	72005	2.25	57.2	.584	14.8	15	2.5	1.5	38	22	97	.65	16.6	0.068	1.7	9.63	MW	CG	N
0.720	18.29	72005S	2.25	57.2	.584	14.8	12	2.2	1.2	30	15	66	.65	16.6	0.068	1.7	9.63	SST	CG	N
0.720	18.29	72021	2.25	57.2	.576	14.6	18	3.2	1.4	35	25	110	.71	18.1	0.072	1.8	9.88	MW	CG	N
0.720	18.29	72021S	2.25	57.2	.576	14.6	15	2.7	1.1	27	17	74	.71	18.1	0.072	1.8	9.88	SST	CG	N
0.720	18.29	72046	2.25	57.2	.560	14.2	26	4.6	1.3	33	34	150	.85	21.6	0.080	2.0	10.6	MW	CG	N
0.720	18.29	72046S	2.25	57.2	.560	14.2	22	3.9	1.0	26	23	100	.85	21.6	0.080	2.0	10.6	SST	CG	N
0.720	18.29	72064	2.25	57.2	.558	14.2	28	5.0	1.2	31	35	155	.84	21.3	0.081	2.1	10.4	MW	CG	N
0.720	18.29	72064S	2.25	57.2	.558	14.2	24	4.2	.97	25	23	104	.84	21.3	0.081	2.1	10.4	SST	CG	N
0.720	18.29	72077	2.25	57.2	.550	14.0	39	6.8	1.0	26	40	179	.82	20.8	0.085	2.2	9.63	MW	CG	N
0.720	18.29	72077S	2.25	57.2	.550	14.0	33	5.8	.82	21	27	120	.82	20.8	0.085	2.2	9.63	SST	CG	N
0.720	18.29	72088	2.25	57.2	.538	13.														



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.720	18.29	72048S	2.50	63.5	.560	14.2	20	3.5	1.1	29	23	100	.93	23.6	0.080	2.0	11.6	SST	CG	N
0.720	18.29	72065	2.50	63.5	.558	14.2	25	4.4	1.4	35	35	155	.92	23.4	0.081	2.1	11.4	MW	CG	N
0.720	18.29	72065S	2.50	63.5	.558	14.2	21	3.8	1.1	28	23	104	.92	23.4	0.081	2.1	11.4	SST	CG	N
0.720	18.29	72078	2.50	63.5	.550	14.0	35	6.1	1.2	30	40	179	.89	22.7	0.085	2.2	10.5	MW	CG	N
0.720	18.29	72078S	2.50	63.5	.550	14.0	29	5.1	.92	23	27	120	.89	22.7	0.085	2.2	10.5	SST	CG	N
0.720	18.29	72090	2.50	63.5	.538	13.7	38	6.7	1.2	32	47	210	1.13	28.6	0.091	2.3	12.4	MW	CG	N
0.720	18.29	72090S	2.50	63.5	.538	13.7	32	5.7	.97	25	31	139	1.13	28.6	0.091	2.3	12.4	SST	CG	N
0.720	18.29	72105	2.50	63.5	.528	13.4	58	10	.96	24	55	245	1.03	26.2	0.096	2.4	10.8	MW	CG	N
0.720	18.29	72105S	2.50	63.5	.528	13.4	49	8.6	.75	19	37	163	1.03	26.2	0.096	2.4	10.8	SST	CG	N
0.720	18.29	72118	2.50	63.5	.510	13.0	84	15	.86	22	72	318	1.16	29.3	0.105	2.7	11.0	MW	CG	N
0.720	18.29	72118S	2.50	63.5	.510	13.0	71	12	.67	17	47	211	1.16	29.3	0.105	2.7	11.0	SST	CG	N
0.720	18.29	72131	2.50	63.5	.496	12.6	107	19	.78	20	83	371	1.27	32.4	0.112	2.8	11.4	MW	CG	N
0.720	18.29	72131S	2.50	63.5	.496	12.6	91	16	.60	15	54	242	1.27	32.4	0.112	2.8	11.4	SST	CG	N
0.720	18.29	71936	2.75	69.9	.610	15.5	6.2	1.1	1.9	48	12	52	.51	12.9	0.055	1.4	9.25	MW	CG	N
0.720	18.29	71936S	2.75	69.9	.610	15.5	5.2	.92	1.5	38	7.9	35	.51	12.9	0.055	1.4	9.25	SST	CG	N
0.720	18.29	71948	2.75	69.9	.602	15.3	7.2	1.3	2.0	51	14	64	.61	15.5	0.059	1.5	10.4	MW	CG	N
0.720	18.29	71948S	2.75	69.9	.602	15.3	6.1	1.1	1.6	40	9.7	43	.61	15.5	0.059	1.5	10.4	SST	CG	N
0.720	18.29	71961	2.75	69.9	.594	15.1	8.9	1.6	2.0	50	17	78	.69	17.6	0.063	1.6	11.0	MW	CG	N
0.720	18.29	71961S	2.75	69.9	.594	15.1	7.6	1.3	1.6	40	12	53	.69	17.6	0.063	1.6	11.0	SST	CG	N
0.720	18.29	71972	2.75	69.9	.590	15.0	10	1.8	1.9	48	19	85	.72	18.4	0.065	1.7	11.1	MW	CG	N
0.720	18.29	71972S	2.75	69.9	.590	15.0	8.5	1.5	1.5	39	13	58	.72	18.4	0.065	1.7	11.1	SST	CG	N
0.720	18.29	72009	2.75	69.9	.584	14.8	12	2.0	1.9	47	22	97	.78	19.9	0.068	1.7	11.5	MW	CG	N
0.720	18.29	72009S	2.75	69.9	.584	14.8	9.9	1.7	1.5	38	15	66	.78	19.9	0.068	1.7	11.5	SST	CG	N
0.720	18.29	72023	2.75	69.9	.576	14.6	15	2.6	1.7	43	25	110	.84	21.3	0.072	1.8	11.6	MW	CG	N
0.720	18.29	72023S	2.75	69.9	.576	14.6	12	2.2	1.3	34	17	74	.84	21.3	0.072	1.8	11.6	SST	CG	N
0.720	18.29	72050	2.75	69.9	.560	14.2	21	3.7	1.6	41	34	150	1.02	25.9	0.080	2.0	12.8	MW	CG	N
0.720	18.29	72050S	2.75	69.9	.560	14.2	18	3.1	1.3	32	23	100	1.02	25.9	0.080	2.0	12.8	SST	CG	N
0.720	18.29	72066	2.75	69.9	.558	14.2	23	4.0	1.5	39	35	155	1.00	25.5	0.081	2.1	12.4	MW	CG	N
0.720	18.29	72066S	2.75	69.9	.558	14.2	19	3.4	1.2	31	23	104	1.00	25.5	0.081	2.1	12.4	SST	CG	N
0.720	18.29	72079	2.75	69.9	.550	14.0	31	5.5	1.3	33	40	179	.97	24.6	0.085	2.2	11.4	MW	CG	N
0.720	18.29	72079S	2.75	69.9	.550	14.0	27	4.6	1.0	26	27	120	.97	24.6	0.085	2.2	11.4	SST	CG	N
0.720	18.29	72092	2.75	69.9	.538	13.7	34	6.0	1.4	35	47	210	1.23	31.2	0.091	2.3	13.5	MW	CG	N
0.720	18.29	72092S	2.75	69.9	.538	13.7	29	5.1	1.1	27	31	139	1.23	31.2	0.091	2.3	13.5	SST	CG	N
0.720	18.29	72106	2.75	69.9	.528	13.4	52	9.1	1.1	27	55	245	1.12	28.3	0.096	2.4	11.6	MW	CG	N
0.720	18.29	72106S	2.75	69.9	.528	13.4	44	7.8	.83	21	37	163	1.12	28.3	0.096	2.4	11.6	SST	CG	N
0.720	18.29	72119	2.75	69.9	.510	13.0	75	13	.95	24	72	318	1.26	32.0	0.105	2.7	12.0	MW	CG	N
0.720	18.29	72119S	2.75	69.9	.510	13.0	64	11	.74	19	47	211	1.26	32.0	0.105	2.7	12.0	SST	CG	N
0.720	18.29	72132	2.75	69.9	.496	12.6	97	17	.86	22	83	371	1.39	35.2	0.112	2.8	12.4	MW	CG	N
0.720	18.29	72132S	2.75	69.9	.496	12.6	82	14	.66	17	54	242	1.39	35.2	0.112	2.8	12.4	SST	CG	N
0.720	18.29	71937	3.00	76.2	.610	15.5	5.6	.98	2.1	53	12	52	.55	14.0	0.055	1.4	10.0	MW	CG	N
0.720	18.29	71937S	3.00	76.2	.610	15.5	4.8	.83	1.7	42	7.9	35	.55	14.0	0.055	1.4	10.0	SST	CG	N
0.720	18.29	71950	3.00	76.2	.602	15.3	6.6	1.2	2.2	55	14	64	.66	16.7	0.059	1.5	11.1	MW	CG	N
0.720	18.29	71950S	3.00	76.2	.602	15.3	5.6	.98	1.7	44	9.7	43	.66	16.7	0.059	1.5	11.1	SST	CG	N
0.720	18.29	71962	3.00	76.2	.594	15.1	8.1	1.4	2.2	55	17	78	.75	19.0	0.063	1.6	11.9	MW	CG	N
0.720	18.29	71962S	3.00	76.2	.594	15.1	6.9	1.2	1.7	44	12	53	.75	19.0	0.063	1.6	11.9	SST	CG	N
0.720	18.29	71973	3.00	76.2	.590	15.0	9.1	1.6	2.1	53	19	85	.78	19.8	0.065	1.7	12.0	MW	CG	N
0.720	18.29	71973S	3.00	76.2	.590	15.0	7.8	1.4	1.7	42	13	58	.78	19.8	0.065	1.7	12.0	SST	CG	N
0.720	18.29	71985	3.00	76.2	.586	14.9	11	1.8	2.0	51	21	93	.80	20.2	0.067	1.7	11.9	MW	CG	N
0.720	18.29	71985S	3.00	76.2	.586	14.9	8.9	1.6	1.6	40	14	63	.80	20.2	0.067	1.7	11.9	SST	CG	N
0.720	18.29	72011	3.00	76.2	.584	14.8	11	1.9	2.0	52	22	97	.84	21.4	0.068	1.7	12.4	MW	CG	N
0.720	18.29	72011S	3.00	76.2	.584	14.8	9.1	1.6	1.6	41	15	66	.84	21.4	0.068	1.7	12.4	SST	CG	N
0.720	18.29	72024	3.00	76.2	.576	14.6	13	2.3	1.9	47	25	110	.91	23.1	0.072	1.8	12.6	MW	CG	N
0.720	18.29	72024S	3.00	76.2	.576	14.6	11	2.0	1.5	37	17	74	.91	23.1	0.072	1.8	12.6	SST	CG	N
0.720	18.29	72052	3.00	76.2	.560	14.2	19	3.3	1.8	45	34	150	1.10	27.9	0.080	2.0	13.8	MW	CG	N
0.720	18.29	72052S	3.00	76.2	.560	14.2	16	2.8	1.4	35	23	100	1.10	27.9	0.080	2.0	13.8	SST	CG	N
0.720	18.29	72067	3.00	76.2	.558	14.2	21	3.6	1.7	43	35	155	1.08	27.5	0.081	2.1	13.4	MW	CG	N
0.720	18.29	720672																		



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.720	18.29	72013S	3.50	88.9	.584	14.8	7.7	1.4	1.9	49	15	66	.96	24.4	0.068	1.7	14.1	SST	CG	N
0.720	18.29	72026	3.50	88.9	.576	14.6	11	2.0	2.2	56	25	110	1.05	26.7	0.072	1.8	14.6	MW	CG	N
0.720	18.29	72026S	3.50	88.9	.576	14.6	9.6	1.7	1.7	44	17	74	1.05	26.7	0.072	1.8	14.6	SST	CG	N
0.720	18.29	72054	3.50	88.9	.560	14.2	16	2.9	2.1	52	34	150	1.26	32.0	0.080	2.0	15.8	MW	CG	N
0.720	18.29	72054S	3.50	88.9	.560	14.2	14	2.4	1.6	41	23	100	1.26	32.0	0.080	2.0	15.8	SST	CG	N
0.720	18.29	72068	3.50	88.9	.558	14.2	18	3.1	2.0	50	35	155	1.26	31.9	0.081	2.1	15.5	MW	CG	N
0.720	18.29	72068S	3.50	88.9	.558	14.2	15	2.6	1.6	40	23	104	1.26	31.9	0.081	2.1	15.5	SST	CG	N
0.720	18.29	72081	3.50	88.9	.550	14.0	24	4.2	1.7	42	40	179	1.20	30.5	0.085	2.2	14.1	MW	CG	N
0.720	18.29	72081S	3.50	88.9	.550	14.0	21	3.6	1.3	33	27	120	1.20	30.5	0.085	2.2	14.1	SST	CG	N
0.720	18.29	72096	3.50	88.9	.538	13.7	27	4.7	1.8	45	47	210	1.54	39.0	0.091	2.3	16.9	MW	CG	N
0.720	18.29	72096S	3.50	88.9	.538	13.7	23	4.0	1.4	35	31	139	1.54	39.0	0.091	2.3	16.9	SST	CG	N
0.720	18.29	72108	3.50	88.9	.528	13.4	40	7.1	1.4	35	55	245	1.39	35.4	0.096	2.4	14.5	MW	CG	N
0.720	18.29	72108S	3.50	88.9	.528	13.4	34	6.0	1.1	27	37	163	1.39	35.4	0.096	2.4	14.5	SST	CG	N
0.720	18.29	72121	3.50	88.9	.510	13.0	58	10	1.2	31	72	318	1.56	39.7	0.105	2.7	14.9	MW	CG	N
0.720	18.29	72121S	3.50	88.9	.510	13.0	49	8.7	.96	24	47	211	1.56	39.7	0.105	2.7	14.9	SST	CG	N
0.720	18.29	72134	3.50	88.9	.496	12.6	75	13	1.1	28	83	371	1.74	44.1	0.112	2.8	15.5	MW	CG	N
0.720	18.29	72134S	3.50	88.9	.496	12.6	63	11	.86	22	54	242	1.74	44.1	0.112	2.8	15.5	SST	CG	N
0.720	18.29	72027	4.00	101.6	.576	14.6	9.9	1.7	2.5	64	25	110	1.18	29.9	0.072	1.8	16.4	MW	CG	N
0.720	18.29	72027S	4.00	101.6	.576	14.6	8.4	1.5	2.0	50	17	74	1.18	29.9	0.072	1.8	16.4	SST	CG	N
0.720	18.29	72056	4.00	101.6	.560	14.2	14	2.5	2.4	61	34	150	1.43	36.3	0.080	2.0	17.9	MW	CG	N
0.720	18.29	72056S	4.00	101.6	.560	14.2	12	2.1	1.9	48	23	100	1.43	36.3	0.080	2.0	17.9	SST	CG	N
0.720	18.29	72069	4.00	101.6	.558	14.2	15	2.7	2.3	58	35	155	1.42	36.0	0.081	2.1	17.5	MW	CG	N
0.720	18.29	72069S	4.00	101.6	.558	14.2	13	2.3	1.8	46	23	104	1.42	36.0	0.081	2.1	17.5	SST	CG	N
0.720	18.29	72082	4.00	101.6	.550	14.0	21	3.7	1.9	49	40	179	1.36	34.5	0.085	2.2	16.0	MW	CG	N
0.720	18.29	72082S	4.00	101.6	.550	14.0	18	3.1	1.5	38	27	120	1.36	34.5	0.085	2.2	16.0	SST	CG	N
0.720	18.29	72109	4.00	101.6	.528	13.4	35	6.1	1.6	40	55	245	1.57	39.9	0.096	2.4	16.4	MW	CG	N
0.720	18.29	72109S	4.00	101.6	.528	13.4	32	5.2	1.2	31	37	163	1.57	39.9	0.097	2.4	16.4	SST	CG	N
0.720	18.29	72122	4.00	101.6	.510	13.0	51	8.8	1.4	36	72	318	1.77	45.0	0.105	2.7	16.9	MW	CG	N
0.720	18.29	72122S	4.00	101.6	.510	13.0	43	7.5	1.1	28	47	211	1.77	45.0	0.105	2.7	16.9	SST	CG	N
0.720	18.29	72135	4.00	101.6	.496	12.6	65	11	1.3	33	83	371	1.96	49.8	0.112	2.8	17.5	MW	CG	N
0.720	18.29	72135S	4.00	101.6	.496	12.6	55	9.6	.99	25	54	242	1.96	49.8	0.112	2.8	17.5	SST	CG	N
0.734	18.64	XX-36	.50	12.7	.626	15.9	19	3.4	.28	7.2	5.5	25	.22	5.5	0.054	1.4	4.00	SPR	CG	Z
0.734	18.64	S-3203	.56	14.3	.544	13.8	265	46	.13	3.3	35	155	.33	8.4	0.095	2.4	3.50	SST	CG	N
0.734	18.64	B-64	.63	15.9	.664	16.9	5.5	.96	.39	10	2.2	9.6	.14	3.6	0.035	0.9	3.00	SST	C	N
0.734	18.64	AA-54	.63	15.9	.574	14.6	107	19	.21	5.3	22	99	.30	7.6	0.080	2.0	3.75	SST	CG	N
0.734	18.64	II-67	.66	16.7	.614	15.6	18	3.2	.30	7.5	5.3	24	.36	9.1	0.060	1.5	5.00	SST	C	N
0.734	18.64	S-1220	.69	17.4	.524	13.3	305	53	.15	3.9	47	207	.42	10.7	0.105	2.7	4.00	SST	CG	N
0.734	18.64	S-1319	.69	17.4	.494	12.5	640	112	.10	2.6	65	291	.45	11.4	0.120	3.0	3.75	SST	CG	N
0.734	18.64	NN-98	.72	18.2	.614	15.6	15	2.7	.36	9.1	5.4	24	.36	9.1	0.060	1.5	6.00	SPR	CG	N
0.734	18.64	S-164	.72	18.2	.574	14.6	93	16	.24	6.0	22	99	.40	10.2	0.080	2.0	4.00	SST	C	N
0.734	18.64	CC-99	.75	19.1	.694	17.6	.08	.01	.56	14	.05	.21	.19	4.8	0.020	0.5	8.50	SST	C	N
0.734	18.64	BB-75	.75	19.1	.656	16.7	2.9	.50	.52	13	1.5	6.6	.23	5.9	0.039	1.0	5.00	SST	C	N
0.734	18.64	A10-62	.75	19.1	.654	16.6	3.3	.58	.55	14	1.8	8.1	.20	5.1	0.040	1.0	5.00	SST	CG	N
0.734	18.64	S-1475	.75	19.1	.646	16.4	3.6	.62	.44	11	1.6	7.0	.31	7.8	0.044	1.1	6.00	SST	C	N
0.734	18.64	11176	.75	19.1	.638	16.2	14	2.4	.40	10	5.5	25	.22	5.5	0.048	1.2	3.50	SST	C	N
0.734	18.64	3867	.75	19.1	.630	16.0	17	2.9	.42	11	7.0	31	.26	6.6	0.052	1.3	4.00	SPR	C	Z
0.734	18.64	B12-38	.75	19.1	.606	15.4	29	5.1	.38	9.7	11	50	.37	9.3	0.064	1.6	4.75	SPR	C	Z
0.734	18.64	S-3085	.88	22.2	.600	15.2	34	5.9	.41	10	14	62	.30	7.7	0.067	1.7	4.50	SST	CG	N
0.734	18.64	S-1343	.88	22.2	.574	14.6	46	8.0	.40	10	18	80	.48	12.2	0.080	2.0	6.00	SST	CG	N
0.734	18.64	V-26	.94	23.8	.650	16.5	4.5	.79	.69	17	3.1	14	.25	6.4	0.042	1.1	5.00	SPR	C	GI
0.734	18.64	S-310	1.00	25.4	.600	15.2	28	5.0	.49	12	14	62	.34	8.5	0.067	1.7	5.00	SST	CG	N
0.734	18.64	3796	1.00	25.4	.590	15.0	44	7.8	.39	9.9	17	77	.36	9.1	0.072	1.8	5.00	HD	CG	GI
0.734	18.64	S-340	1.09	27.8	.380	9.7	2069	362	.09	2.2	180	800	.97	24.7	0.177	4.5	5.50	SST	CG	N
0.734	18.64	S-1373	1.13	28.6	.508	12.9	213	37	.26	6.6	55	244	.79	20.1	0.113	2.9	6.00	SST	CG	N
0.734	18.64	S-403	1.16	29.4	.636	16.2	4.4	.77	.81	20	3.5	16	.35	8.9	0.049	1.2	7.00	SST	CG	N
0.734	18.64	11820	1.19	30.2	.562	14.3	72	13	.40	10	29	130	.52	13.1	0.086	2.2	6.00	SPR	CG	Z
0.734	18.64	S-263	1.19	30.2	.494	12.5	228	40	.29	7.3	65	291	.84	21.3	0.120	3.0	7.00	SST	CG	N
0.73																				



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.734	18.64	A-42	1.75	44.5	.584	14.8	26	4.6	.74	19	20	87	.60	15.2	0.075	1.9	8.00	SPR	CG	N
0.734	18.64	3347	1.88	47.6	.594	15.1	18	3.2	.88	22	16	71	.60	15.1	0.070	1.8	8.50	SPR	CG	Z
0.734	18.64	S-248	1.91	48.4	.550	14.0	35	6.0	.80	20	28	123	1.10	28.0	0.092	2.3	12.0	SST	CG	N
0.734	18.64	S-417	2.00	50.8	.552	14.0	33	5.9	.92	23	31	137	1.06	26.9	0.091	2.3	11.8	SST	CG	N
0.734	18.64	10530	2.06	52.4	.590	15.0	16	2.7	1.1	28	17	77	.83	21.0	0.072	1.8	10.5	SPR	C	Z
0.734	18.64	11693	2.09	53.2	.610	15.5	7.6	1.3	1.4	35	11	47	.70	17.7	0.062	1.6	11.3	SPR	CG	Z
0.734	18.64	10981	2.19	55.6	.590	15.0	15	2.6	1.1	28	16	72	.72	18.3	0.072	1.8	10.0	SST	CG	N
0.734	18.64	S-493	2.34	59.5	.532	13.5	53	9.3	.79	20	42	185	1.18	29.9	0.101	2.6	11.7	SST	CG	N
0.734	18.64	10871	2.44	61.9	.558	14.2	36	6.2	.88	22	31	139	.97	24.6	0.088	2.2	11.0	SPR	CG	N
0.734	18.64	10886	2.50	63.5	.614	15.6	6.1	1.1	1.8	45	11	47	.72	18.3	0.060	1.5	12.0	SPR	CG	Z
0.734	18.64	1663	2.63	66.7	.574	14.6	16	2.8	1.3	34	22	97	1.28	32.5	0.080	2.0	15.0	SPR	C	Z
0.734	18.64	S-1224	2.69	68.2	.626	15.9	2.8	.49	1.9	49	5.4	24	.76	19.2	0.054	1.4	14.0	SST	CG	N
0.734	18.64	3365	2.75	69.9	.610	15.5	7.0	1.2	1.7	43	12	52	.81	20.5	0.062	1.6	12.0	SPR	C	GI
0.734	18.64	S-1503	2.94	74.6	.646	16.4	.85	.15	2.1	54	1.8	8.0	.83	21.0	0.044	1.1	18.8	SST	CG	N
0.734	18.64	2747	2.94	74.6	.464	11.8	185	32	.53	13	97	434	1.89	48.0	0.135	3.4	14.0	SPR	CG	Z
0.734	18.64	11333	3.00	76.2	.578	14.7	18	3.2	1.2	30	22	98	1.03	26.3	0.078	2.0	12.3	HD	C	Z
0.734	18.64	B18-181	3.00	76.2	.554	14.1	17	3.0	1.2	30	21	93	1.80	45.7	0.090	2.3	20.0	SST	CG	N
0.734	18.64	B11-44	3.25	82.6	.622	15.8	6.5	1.1	1.3	34	8.7	39	.56	14.2	0.056	1.4	9.00	SPR	C	N
0.734	18.64	3753	3.50	88.9	.650	16.5	1.6	.28	2.5	63	4.0	18	.48	12.3	0.042	1.1	10.5	SPR	C	Z
0.734	18.64	4126	3.50	88.9	.640	16.3	1.6	.28	2.7	69	4.4	19	.78	19.7	0.047	1.2	15.5	HD	C	Z
0.734	18.64	12723	3.50	88.9	.616	15.6	4.0	.71	2.6	65	10	46	.94	24.0	0.059	1.5	16.0	MW	CG	GI
0.734	18.64	4190	3.50	88.9	.604	15.3	9.5	1.7	1.4	36	14	60	.72	18.2	0.065	1.7	11.0	SPR	CG	Z
0.734	18.64	1555	3.50	88.9	.590	15.0	10	1.8	1.7	43	17	77	1.15	29.3	0.072	1.8	15.0	SPR	C	Z
0.734	18.64	S-1430	3.56	90.5	.574	14.6	8.3	1.5	1.6	40	13	58	2.00	50.8	0.080	2.0	24.0	SST	C	N
0.734	18.64	3876	3.69	93.6	.584	14.8	11	1.9	1.8	47	20	87	1.28	32.4	0.075	1.9	17.0	SPR	CG	Z
0.734	18.64	11937	4.63	117.5	.538	13.7	25	4.3	1.7	43	41	183	2.25	57.3	0.098	2.5	23.0	SPR	CG	Z
0.734	18.64	11540	5.00	127.0	.614	15.6	3.6	.63	3.0	76	11	47	1.20	30.5	0.060	1.5	19.0	SPR	C	Z
0.734	18.64	11392	6.13	155.6	.484	12.3	55	9.7	1.5	37	81	358	3.75	95.3	0.125	3.2	30.0	SPR	CG	Z
0.734	18.64	11885	6.31	160.3	.528	13.4	23	4.1	2.0	52	48	212	3.04	77.2	0.103	2.6	29.5	SPR	CG	N
0.734	18.64	12609	6.38	161.9	.708	18.0	.55	9.7	2.0	51	112	497	3.75	95	0.013	0.3	30	MW	C	N
0.734	18.64	4158	11.5	292.1	.534	13.6	13	2.3	3.3	85	44	194	4.60	116.8	0.100	2.5	45.0	SPR	C	Z
0.750	19.05	B4-20	.50	12.7	.650	16.5	21	3.7	.29	7.4	6.1	27	.16	4.1	0.050	1.3	3.25	SPR	CG	N
0.750	19.05	2518	.50	12.7	.642	16.3	24	4.2	.31	7.9	7.5	33	.19	4.8	0.054	1.4	3.50	HD	CG	Z
0.750	19.05	B2-57	.56	14.3	.688	17.5	2.9	.50	.43	11	1.2	5.5	.13	3.4	0.031	0.8	3.25	MW	C	Z
0.750	19.05	S-1345	.56	14.3	.674	17.1	2.9	.51	.39	9.9	1.1	5.0	.17	4.3	0.038	1.0	4.50	SST	CG	N
0.750	19.05	00-84	.56	14.3	.650	16.5	9.5	1.7	.27	7.0	2.6	12	.29	7.3	0.050	1.3	4.75	SPR	C	Z
0.750	19.05	CC-79	.56	14.3	.590	15.0	98	17	.24	6.0	23	103	.32	8.1	0.080	2.0	4.00	SPR	CG	N
0.750	19.05	B15-66	.59	15.1	.670	17.0	4.1	.72	.41	10	1.7	7.6	.18	4.6	0.040	1.0	4.50	SPR	CG	N
0.750	19.05	2665	.59	15.1	.586	14.9	193	34	.13	3.3	25	111	.26	6.5	0.082	2.1	3.25	SPR	CG	Z
0.750	19.05	S-238	.63	15.9	.550	14.0	182	32	.18	4.4	32	142	.45	11.4	0.100	2.5	4.50	SST	CG	N
0.750	19.05	12559	.70	17.9	.610	15.5	40	7.0	.37	9.4	15	66	.33	8.5	0.070	1.8	4.75	SPR	CG	N
0.750	19.05	S-1321	.75	19.1	.656	16.7	8.8	1.5	.52	13	4.5	20	.24	6.0	0.047	1.2	4.00	SST	C	N
0.750	19.05	12581	.75	19.1	.650	16.5	13	2.3	.46	12	6.1	27	.25	6.4	0.050	1.3	4.00	SPR	C	N
0.750	19.05	KK-93	.75	19.1	.636	16.2	13	2.3	.44	11	5.7	25	.31	8.0	0.057	1.4	5.50	SPR	CG	N
0.750	19.05	GG-64	.75	19.1	.430	10.9	2294	402	.07	1.7	151	671	.64	16.3	0.160	4.1	4.00	SPR	CG	N
0.750	19.05	10140	.81	20.6	.616	15.6	45	8.0	.32	8.1	14	64	.27	6.8	0.067	1.7	4.00	SPR	CG	Z
0.750	19.05	S-1301	.88	22.2	.642	16.3	16	2.8	.46	12	7.2	32	.22	5.5	0.054	1.4	4.00	SST	C	N
0.750	19.05	A14-67	.88	22.2	.636	16.2	23	4.0	.39	10	9.0	40	.23	5.8	0.057	1.4	4.00	SPR	CG	GI
0.750	19.05	10448	.88	22.2	.606	15.4	41	7.2	.41	10	17	76	.36	9.1	0.072	1.8	5.00	SPR	CG	Z
0.750	19.05	2590	.89	22.6	.590	15.0	39	6.9	.33	8.4	13	57	.56	14.2	0.080	2.0	7.00	HD	CG	Z
0.750	19.05	12584	.91	23.0	.510	13.0	397	70	.18	4.5	70	313	.60	15.2	0.120	3.0	5.00	SPR	CG	N
0.750	19.05	N-137	.94	23.8	.672	17.1	2.3	.41	.70	18	1.6	7.2	.23	5.9	0.039	1.0	6.00	SPR	C	N
0.750	19.05	B15-40	.94	23.8	.658	16.7	6.7	1.2	.72	18	4.8	21	.22	5.5	0.046	1.2	4.75	SPR	CG	Z
0.750	19.05	B1-65	.94	23.8	.624	15.8	25	4.3	.46	12	11	51	.35	8.8	0.063	1.6	4.50	SST	CG	N
0.750	19.05	3033	.94	23.8	.540	13.7	326	57	.15	3.8	49	219	.42	10.7	0.105	2.7	4.00	SPR	CG	Z
0.750	19.05	2602	.97	24.6	.646	16.4	7.3	1.3	.64	16	4.7	21	.33	8.3	0.052	1.3	6.25	HD	CG	Z
0.750	19.05	S-3115	1.00	25.4	.668	17.0	5.0	.87	.68	17	3.4	15	.21	5.2	0.041	1.0				



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.750	19.05	11701	1.13	28.6	.496	12.6	387	68	.21	5.4	83	368	.76	19.4	0.127	3.2	6.00	SPR	CG	Z
0.750	19.05	S-1448	1.13	28.6	.480	12.2	446	78	.19	4.9	86	383	.81	20.6	0.135	3.4	6.00	SST	CG	N
0.750	19.05	B17-121	1.16	29.4	.620	15.7	23	4.0	.58	15	13	59	.36	9.1	0.065	1.7	5.50	SPR	CG	N
0.750	19.05	10933	1.19	30.2	.626	15.9	16	2.9	.71	18	12	51	.43	11.0	0.062	1.6	6.00	SPR	C	N
0.750	19.05	HH-7	1.19	30.2	.570	14.5	73	13	.40	10	29	130	.54	13.7	0.090	2.3	6.00	SST	CG	N
0.750	19.05	S-1537	1.19	30.2	.514	13.1	192	34	.32	8.1	61	272	.83	21.0	0.118	3.0	7.00	SST	CG	N
0.750	19.05	12198	1.22	31.0	.570	14.5	55	9.6	.50	13	27	121	.72	18.3	0.090	2.3	8.00	SPR	CG	Z
0.750	19.05	S-392	1.25	31.8	.626	15.9	16	2.8	.67	17	11	48	.40	10.2	0.062	1.6	5.50	SST	C	N
0.750	19.05	S-1287	1.25	31.8	.616	15.6	23	4.0	.60	15	14	61	.37	9.4	0.067	1.7	5.50	SST	CG	N
0.750	19.05	EE-73	1.25	31.8	.590	15.0	36	6.2	.65	17	23	103	.60	15.2	0.080	2.0	7.50	SPR	CG	Z
0.750	19.05	KK-72	1.25	31.8	.530	13.5	146	26	.37	9.5	55	243	.83	21.0	0.110	2.8	7.50	SPR	CG	N
0.750	19.05	B1-69	1.28	32.5	.614	15.6	28	4.8	.55	14	15	67	.37	9.5	0.068	1.7	5.50	SPR	CG	N
0.750	19.05	S-1634	1.31	33.3	.688	17.5	1.1	.18	1.2	29	1.2	5.4	.16	3.9	0.031	0.8	5.00	SST	CG	N
0.750	19.05	10637	1.31	33.3	.622	15.8	23	4.0	.55	14	13	56	.40	10.2	0.064	1.6	5.25	SPR	C	Z
0.750	19.05	4284	1.31	33.3	.616	15.6	19	3.4	.76	19	14	64	.45	11.5	0.067	1.7	6.75	SPR	CG	Z
0.750	19.05	12259	1.31	33.3	.616	15.6	18	3.2	.80	20	14	64	.47	11.9	0.067	1.7	7.00	SPR	CG	Z
0.750	19.05	11798	1.34	34.1	.652	16.6	6.0	1.1	1.0	25	6.0	27	.34	8.7	0.049	1.2	6.00	SPR	C	N
0.750	19.05	12230	1.34	34.1	.608	15.4	26	4.5	.63	16	16	73	.46	11.7	0.071	1.8	6.50	SPR	CG	Z
0.750	19.05	12224	1.38	34.9	.650	16.5	6.5	1.1	.93	24	6.1	27	.30	7.6	0.050	1.3	6.00	SPR	CG	N
0.750	19.05	S-439	1.38	34.9	.640	16.3	7.7	1.4	.98	25	7.6	34	.36	9.1	0.055	1.4	6.50	SST	CG	N
0.750	19.05	3064	1.38	34.9	.256	6.5	12936	2265	.03	.84	427	1901	1.30	32.9	0.247	6.3	5.25	SPR	CG	Z
0.750	19.05	A11-64	1.41	35.7	.648	16.5	6.3	1.1	.96	24	6.1	27	.31	7.8	0.051	1.3	6.00	SST	CG	N
0.750	19.05	B7-51	1.41	35.7	.640	16.3	10	1.8	.77	20	8.1	36	.32	8.0	0.055	1.4	5.75	SPR	CG	Z
0.750	19.05	B18-173	1.44	36.5	.630	16.0	13	2.2	.78	20	9.8	44	.36	9.1	0.060	1.5	6.00	SST	CG	N
0.750	19.05	3824	1.44	36.5	.626	15.9	16	2.9	.71	18	12	51	.37	9.4	0.062	1.6	6.00	HD	CG	Z
0.750	19.05	11516	1.50	38.1	.682	17.3	.87	.15	1.2	30	1.0	4.6	.31	7.8	0.034	0.9	8.00	SPR	C	Z
0.750	19.05	12551	1.50	38.1	.626	15.9	12	2.1	.97	25	12	51	.53	13.4	0.062	1.6	7.50	HD	C	N
0.750	19.05	S-777	1.50	38.1	.624	15.8	14	2.5	.79	20	11	51	.46	11.6	0.063	1.6	6.25	SST	C	N
0.750	19.05	S-868	1.50	38.1	.624	15.8	15	2.6	.77	20	11	51	.39	9.8	0.063	1.6	6.00	SST	CG	N
0.750	19.05	12269	1.50	38.1	.620	15.7	18	3.1	.70	18	12	55	.46	11.6	0.065	1.7	6.00	SST	C	N
0.750	19.05	S-780	1.50	38.1	.606	15.4	24	4.2	.66	17	16	71	.54	13.7	0.072	1.8	6.50	SST	C	N
0.750	19.05	M-104	1.50	38.1	.572	14.5	48	8.4	.66	17	32	141	.76	19.2	0.089	2.3	8.50	SPR	CG	Z
0.750	19.05	11504	1.50	38.1	.570	14.5	77	14	.41	10	31	140	.65	16.6	0.090	2.3	6.25	SPR	CG	Z
0.750	19.05	3165	1.50	38.1	.51	12.9	206	36	.34	8.6	70.0	311.4	.94	23.8	0.120	3.1	7.80	SPR	CG	Z
0.750	19.05	3352	1.63	41.3	.630	16.0	10	1.8	1.0	26	10	46	.51	13.0	0.060	1.5	7.50	SPR	C	Z
0.750	19.05	GG-78	1.63	41.3	.530	13.5	115	20	.48	12	55	243	.99	25.1	0.110	2.8	9.00	SPR	CG	Z
0.750	19.05	FF-30	1.63	41.3	.490	12.4	278	49	.28	7.1	77	344	.98	24.8	0.130	3.3	7.50	SST	CG	N
0.750	19.05	11946	1.72	43.6	.490	12.4	287	50	.30	7.6	86	382	1.04	26.4	0.130	3.3	8.00	SPR	CG	Z
0.750	19.05	2855	1.75	44.5	.684	17.4	.71	.12	1.4	36	1.0	4.5	.31	8.0	0.033	0.8	8.50	HD	C	GI
0.750	19.05	10199	1.75	44.5	.634	16.1	7.0	1.2	1.2	31	8.6	38	.52	13.3	0.058	1.5	9.00	SPR	CG	Z
0.750	19.05	2743	1.75	44.5	.630	16.0	11	2.0	.92	23	10	46	.48	12.2	0.060	1.5	7.00	SPR	C	Z
0.750	19.05	S-778	1.75	44.5	.624	15.8	12	2.1	.93	24	11	51	.50	12.8	0.063	1.6	7.00	SST	C	N
0.750	19.05	S-781	1.75	44.5	.606	15.4	20	3.4	.81	21	16	71	.61	15.5	0.072	1.8	7.50	SST	C	N
0.750	19.05	A11-37	1.81	46.0	.614	15.6	27	4.8	.52	13	14	63	.35	8.9	0.068	1.7	5.00	SST	CG	N
0.750	19.05	S-1325	1.81	46.0	.500	12.7	156	27	.46	12	72	321	1.25	31.8	0.125	3.2	10.0	SST	CG	N
0.750	19.05	12247	1.84	46.8	.624	15.8	11	1.9	1.1	29	12	54	.60	15.2	0.063	1.6	8.50	SPR	C	Z
0.750	19.05	DD-92	1.88	47.6	.650	16.5	3.5	.61	1.4	36	4.9	22	.48	12.1	0.050	1.3	9.50	SPR	CG	GI
0.750	19.05	EE-62	1.88	47.6	.610	15.5	17	3.0	.93	24	16	70	.60	15.1	0.070	1.8	8.50	SPR	CG	Z
0.750	19.05	B18-198	1.91	48.4	.590	15.0	25	4.4	.92	23	23	103	.86	21.8	0.080	2.0	9.75	SPR	C	GI
0.750	19.05	11495	1.94	49.2	.568	14.4	57	10	.57	14	32	145	.82	20.8	0.091	2.3	8.00	SPR	CG	Z
0.750	19.05	11595	1.94	49.2	.538	13.7	80	14	.63	16	51	226	1.22	31.0	0.106	2.7	10.5	SPR	CG	Z
0.750	19.05	S-951	1.97	50.0	.642	16.3	4.0	.70	1.4	36	5.7	26	.53	13.5	0.054	1.4	10.0	SST	CG	N
0.750	19.05	1585	2.00	50.8	.692	17.6	.24	.04	1.6	40	.38	1.7	.41	10.5	0.029	0.7	13.3	MW	C	Z
0.750	19.05	3340	2.00	50.8	.686	17.4	.65	.11	1.7	43	1.1	4.9	.30	7.5	0.032	0.8	8.25	MW	C	Z
0.750	19.05	12228	2.00	50.8	.654	16.6	3.2	.55	1.5	39	4.8	21	.48	12.2	0.048	1.2	9.00	SPR	C	Z
0.750	19.05	10735	2.00	50.8	.640	16.3	4.9	.86	1.5	37	7.1	32	.55	14.0	0.055	1.4	10.0	SPR	CG	Z
0.750	19.05	10226	2.00	50.8	.626	15.9	10	1.8	1.1	29	12	51	.53	13.4	0.062	1.6	8.50	SPR	CG	Z
0.750	19.05	S-779	2.00	50.8	.624	15.8	11	1.8	1.1	27	11	51	.55	14.						



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.750	19.05	48	2.50	63.5	.540	13.7	59	10	.83	21	49	219	1.37	34.7	0.105	2.7	13.0	HD	CG	Z
0.750	19.05	50	2.50	63.5	.480	12.2	195	34	.49	12	96	426	1.69	42.9	0.135	3.4	12.5	HD	CG	Z
0.750	19.05	12451	2.59	65.9	.536	13.6	81	14	.64	16	52	232	1.15	29.2	0.107	2.7	10.8	SPR	CG	N
0.750	19.05	3472	2.63	66.7	.550	14.0	50	8.7	.86	22	43	190	1.35	34.3	0.100	2.5	12.5	SPR	C	Z
0.750	19.05	1873	2.69	68.2	.590	15.0	15	2.6	1.4	36	21	94	1.28	32.5	0.080	2.0	15.0	HD	C	Z
0.750	19.05	4362	2.69	68.2	.540	13.7	55	9.7	.89	23	49	219	1.44	36.7	0.105	2.7	13.8	SPR	CG	Z
0.750	19.05	12199	2.75	69.9	.640	16.3	4.4	.76	1.9	47	8.1	36	.66	16.8	0.055	1.4	11.0	SPR	C	Z
0.750	19.05	3959	2.75	69.9	.580	14.7	26	4.5	1.1	28	28	123	1.02	25.9	0.085	2.2	12.0	SPR	CG	Z
0.750	19.05	12079	2.78	70.6	.616	15.6	8.3	1.4	1.8	44	14	64	.87	22.1	0.067	1.7	13.0	SPR	CG	GI
0.750	19.05	12696	2.81	71.4	.678	17.2	.72	.13	2.4	61	1.7	7.7	.40	10.1	0.036	0.9	10.0	SST	C	N
0.750	19.05	10602	3.00	76.2	.654	16.6	2.8	.48	2.1	53	5.8	26	.53	13.4	0.048	1.2	10.0	SPR	C	Z
0.750	19.05	S-316	3.00	76.2	.648	16.5	1.8	.31	2.1	54	3.8	17	.87	22.0	0.051	1.3	16.0	SST	C	N
0.750	19.05	S-888	3.00	76.2	.626	15.9	5.2	.90	2.1	53	11	48	.81	20.5	0.062	1.6	13.0	SST	CG	N
0.750	19.05	4219	3.00	76.2	.624	15.8	7.0	1.2	1.7	44	12	54	.82	20.8	0.063	1.6	12.0	SPR	C	Z
0.750	19.05	4255	3.00	76.2	.540	13.7	54	9.5	.91	23	49	219	1.58	40.0	0.105	2.7	14.0	SPR	C	Z
0.750	19.05	44	3.13	79.4	.568	14.4	25	4.4	1.3	33	32	145	1.52	38.7	0.091	2.3	15.8	HD	C	Z
0.750	19.05	11467	3.25	82.6	.580	14.7	16	2.7	1.7	43	27	119	1.55	39.4	0.085	2.2	18.3	SPR	CG	Z
0.750	19.05	831	3.25	82.6	.540	13.7	44	7.7	1.1	28	49	219	1.86	47.3	0.105	2.7	16.8	HD	C	Z
0.750	19.05	3869	3.25	82.6	.500	12.7	82	14	.81	21	67	297	2.44	61.9	0.125	3.2	19.5	SPR	CG	Z
0.750	19.05	10084	3.38	85.7	.638	16.2	3.3	.58	2.5	65	8.5	38	.83	21.0	0.056	1.4	14.8	SPR	CG	GI
0.750	19.05	11377	3.47	88.1	.626	15.9	5.5	.96	2.0	50	11	48	.84	21.3	0.062	1.6	12.5	SST	C	N
0.750	19.05	10061	3.50	88.9	.642	16.3	3.5	.60	2.2	56	7.6	34	.68	17.1	0.054	1.4	12.5	SPR	CG	GI
0.750	19.05	890	3.50	88.9	.590	15.0	14	2.4	1.7	43	23	103	1.38	35.1	0.080	2.0	16.3	HD	C	Z
0.750	19.05	11406	3.50	88.9	.590	15.0	12	2.1	1.8	46	22	97	1.40	35.6	0.080	2.0	16.5	SST	C	N
0.750	19.05	40	3.50	88.9	.568	14.4	22	3.9	1.5	37	32	145	1.68	42.8	0.091	2.3	17.5	HD	C	Z
0.750	19.05	1863	3.50	88.9	.554	14.1	31	5.4	1.3	33	40	179	1.81	46.1	0.098	2.5	17.5	SPR	C	Z
0.750	19.05	12306	3.50	88.9	.520	13.2	65	11	.95	24	62	276	1.96	49.7	0.115	2.9	17.0	SPR	CG	Z
0.750	19.05	41	3.50	88.9	.480	12.2	135	24	.71	18	96	426	2.33	59.1	0.135	3.4	17.3	HD	CG	Z
0.750	19.05	11169	3.56	90.5	.500	12.7	74	13	.87	22	64	287	2.69	68.3	0.125	3.2	21.5	SPR	CG	Z
0.750	19.05	4175	3.63	92.1	.634	16.1	4.1	.72	2.3	59	9.4	42	.87	22.1	0.058	1.5	14.0	SPR	C	Z
0.750	19.05	2781	3.69	93.6	.458	11.6	242	42	.49	13	120	532	2.08	52.8	0.146	3.7	14.3	SPR	CG	Z
0.750	19.05	12255	3.84	97.6	.678	17.2	.66	.12	3.4	87	2.3	10	.43	11.0	0.036	0.9	12.0	SPR	CG	Z
0.750	19.05	3700	3.88	98.4	.558	14.2	26	4.6	1.5	37	38	169	1.80	45.7	0.096	2.4	18.8	SPR	CG	GI
0.750	19.05	12553	4.06	103.1	.590	15.0	14	2.4	1.7	44	23	103	1.32	33.5	0.080	2.0	16.5	SPR	CG	N
0.750	19.05	12250	4.13	104.8	.678	17.2	.66	.12	3.7	94	2.4	11	.43	11.0	0.036	0.9	12.0	SPR	CG	Z
0.750	19.05	11737	4.25	108.0	.568	14.4	17	3.0	1.9	48	32	145	2.00	50.9	0.091	2.3	22.0	SPR	CG	Z
0.750	19.05	12193	4.34	110.3	.578	14.7	18	3.1	1.6	41	29	128	1.46	37.1	0.086	2.2	17.0	SPR	CG	GI
0.750	19.05	3932	4.50	114.3	.616	15.6	4.7	.82	3.1	78	14	63	1.44	36.6	0.067	1.7	21.5	SPR	CG	Z
0.750	19.05	11749	4.50	114.3	.608	15.4	6.5	1.1	2.5	64	16	73	1.49	37.9	0.071	1.8	20.0	SPR	C	Z
0.750	19.05	11782	4.59	116.7	.612	15.5	6.7	1.2	2.4	60	16	70	1.21	30.7	0.069	1.8	17.5	SPR	CG	N
0.750	19.05	10816	4.69	119.0	.654	16.6	1.9	.33	3.1	78	5.8	26	.66	16.8	0.048	1.2	13.8	SPR	CG	GI
0.750	19.05	10060	4.75	120.7	.626	15.9	5.6	.97	2.9	73	16	71	.85	21.7	0.062	1.6	13.8	MW	CG	Z
0.750	19.05	1773	4.75	120.7	.620	15.7	8.4	1.5	1.6	40	13	59	.81	20.7	0.065	1.7	11.5	SPR	C	Z
0.750	19.05	3971	4.88	123.8	.590	15.0	10	1.8	2.3	59	23	103	1.72	43.7	0.080	2.0	21.5	SPR	CG	Z
0.750	19.05	854	5.00	127.0	.480	12.2	93	16	1.0	26	96	426	3.24	82.3	0.135	3.4	24.0	HD	CG	Z
0.750	19.05	12064	5.13	130.2	.602	15.3	6.3	1.1	2.9	74	18	82	1.78	45.1	0.074	1.9	24.0	SPR	CG	Z
0.750	19.05	S-1174	5.25	133.4	.590	15.0	8.1	1.4	2.7	68	22	97	1.84	46.7	0.080	2.0	23.0	SST	CG	N
0.750	19.05	11816	6.00	152.4	.602	15.3	5.8	1.0	3.2	81	18	82	1.92	48.9	0.074	1.9	26.0	SPR	CG	GI
0.750	19.05	875	6.00	152.4	.568	14.4	13	2.2	2.6	66	32	145	2.78	70.5	0.091	2.3	29.5	HD	C	Z
0.750	19.05	871	6.00	152.4	.540	13.7	23	4.0	2.2	55	49	219	3.20	81.3	0.105	2.7	30.5	HD	CG	Z
0.750	19.05	827	6.00	152.4	.510	13.0	40	7.0	1.8	45	70	313	3.84	97.5	0.120	3.0	32.0	HD	CG	Z
0.750	19.05	3122	6.25	158.8	.606	15.4	5.3	.92	3.2	82	17	76	1.91	48.5	0.072	1.8	25.5	SPR	C	Z
0.750	19.05	11413	6.25	158.8	.568	14.4	12	2.2	2.6	66	32	145	2.80	71.1	0.091	2.3	29.8	HD	C	Z
0.750	19.05	3051	6.38	161.9	.540	13.7	25	4.3	2.0	51	49	219	2.97	75.3	0.105	2.7	28.3	SPR	CG	Z
0.750	19.05	11545	7.50	190.5	.568	14.4	8.8	1.5	3.7	93	32	144	3.82	97.1	0.091	2.3	41.0	SPR	CG	Z
0.750	19.05	2905	7.56	192.1	.558	14.2	15	2.6	2.5	64	38	169	2.98	75.6	0.096	2.4	31.0	SPR	CG	Z
0.750	19.05																			




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.765	19.43	HH-76	1.00	25.4	.485	12.3	502	88	.16	4.1	80	357	.84	21.3	0.140	3.6	6.00	SST	CG	N
0.765	19.43	S-3245	1.03	26.2	.685	17.4		4.3 .75	.72	18	3.1	14	.16	4.1	0.040	1.0	4.00	SST	CG	N
0.765	19.43	3682	1.06	27.0	.671	17.0		5.8 1.0	.82	21	4.8	21	.25	6.3	0.047	1.2	5.25	SPR	CG	Z
0.765	19.43	S-1150	1.13	28.6	.525	13.3	322	56	.20	5.0	63	280	.60	15.2	0.120	3.0	5.00	SST	CG	N
0.765	19.43	S-385	1.16	29.4	.695	17.7		1.3 .23	.96	24	1.3	5.7	.20	5.0	0.035	0.9	6.00	SST	C	N
0.765	19.43	3152	1.16	29.4	.551	14.0	165	29	.31	7.9	51	228	.64	16.3	0.107	2.7	6.00	SPR	CG	Z
0.765	19.43	S-187	1.25	31.8	.665	16.9		3.3 .58	.83	21	2.7	12	.43	10.8	0.050	1.3	8.50	SST	CG	N
0.765	19.43	S-1320	1.25	31.8	.641	16.3		7.9 1.4	.71	18	5.6	25	.54	13.8	0.062	1.6	8.75	SST	CG	N
0.765	19.43	B11-26	1.25	31.8	.635	16.1		23 4.0	.56	14	13	58	.34	8.7	0.065	1.7	5.25	SPR	CG	N
0.765	19.43	B12-20	1.25	31.8	.545	13.8	187	33	.29	7.3	54	239	.66	16.8	0.110	2.8	6.00	SPR	CG	Z
0.765	19.43	3771	1.25	31.8	.495	12.6	477	84	.20	5.0	94	419	.81	20.6	0.135	3.4	6.00	SPR	CG	Z
0.765	19.43	12146	1.31	33.3	.585	14.9		51 9.0	.59	15	30	135	.72	18.3	0.090	2.3	8.00	SPR	CG	Z
0.765	19.43	11599	1.41	35.7	.691	17.6		2.1 .37	1.2	30	2.5	11	.23	5.9	0.037	0.9	5.33	SPR	C	Z
0.765	19.43	12122	1.41	35.7	.603	15.3	39	6.8	.61	16	24	105	.57	14.4	0.081	2.1	7.00	SPR	CG	Z
0.765	19.43	S-423	1.41	35.7	.525	13.3	172	30	.37	9.3	63	280	.92	23.2	0.120	3.0	7.75	SST	CG	N
0.765	19.43	2853	1.44	36.5	.663	16.8		5.3 .94	1.1	27	5.8	26	.36	9.1	0.051	1.3	7.00	SPR	CG	Z
0.765	19.43	S-1623	1.47	37.3	.625	15.9	18	3.2	.79	20	14	64	.56	14.2	0.070	1.8	7.00	SST	CG	N
0.765	19.43	S-222	1.50	38.1	.695	17.7		1.2 .21	1.3	32	1.5	6.7	.25	6.2	0.035	0.9	6.00	SST	C	N
0.765	19.43	10915	1.50	38.1	.665	16.9		2.8 .49	.91	23	2.6	11	.59	14.9	0.050	1.3	10.8	SPR	C	N
0.765	19.43	S-1298	1.50	38.1	.629	16.0	18	3.1	.79	20	14	62	.44	11.1	0.068	1.7	6.50	SST	CG	N
0.765	19.43	S-438	1.50	38.1	.621	15.8		17 2.9	.92	23	16	69	.58	14.6	0.072	1.8	8.00	SST	CG	N
0.765	19.43	S-253	1.56	39.7	.525	13.3	164	29	.38	9.7	63	280	.96	24.4	0.120	3.0	8.00	SST	CG	N
0.765	19.43	4304	1.63	41.3	.583	14.8	61	11	.52	13	32	142	.66	16.8	0.091	2.3	7.25	SPR	CG	Z
0.765	19.43	3411	1.63	41.3	.555	14.1	111	19	.44	11	48	215	.79	20.0	0.105	2.7	7.50	SPR	CG	GI
0.765	19.43	NN-80	1.63	41.3	.505	12.8	211	37	.36	9.2	76	338	1.14	28.9	0.130	3.3	8.75	SST	CG	N
0.765	19.43	CC-70	1.75	44.5	.585	14.9		23 4.0	.49	12	11	49	1.26	32.0	0.090	2.3	14.0	SST	CG	N
0.765	19.43	11410	1.81	46.0	.525	13.3	153	27	.45	11	69	307	1.11	28.2	0.120	3.0	9.25	SPR	CG	Z
0.765	19.43	4148	2.00	50.8	.641	16.3		6.8 1.2	1.3	32	8.5	38	.74	18.9	0.062	1.6	11.0	HD	C	Z
0.765	19.43	12164	2.00	50.8	.601	15.3	27	4.8	.90	23	24	109	.86	21.9	0.082	2.1	9.50	SPR	C	Z
0.765	19.43	S-308	2.00	50.8	.515	13.1	212	37	.33	8.5	71	315	.94	23.8	0.125	3.2	7.50	SST	CG	N
0.765	19.43	11803	2.09	53.2	.579	14.7	59	10	.58	15	34	151	.74	18.9	0.093	2.4	8.00	SPR	CG	Z
0.765	19.43	S-433	2.19	55.6	.641	16.3		8.2 1.4	1.3	33	11	47	.60	15.2	0.062	1.6	8.75	SST	CG	N
0.765	19.43	S-909	2.44	61.9	.603	15.3	18	3.2	1.2	30	22	98	.90	22.9	0.081	2.1	11.0	SST	CG	N
0.765	19.43	11713	2.47	62.7	.523	13.3	105	18	.67	17	71	315	1.57	40.0	0.121	3.1	13.0	SPR	CG	Z
0.765	19.43	3439	2.69	68.2	.577	14.7	41	7.2	.85	22	35	156	1.13	28.7	0.094	2.4	11.0	SPR	C	Z
0.765	19.43	B8-53	2.72	69.0	.655	16.6		4.6 .80	1.7	44	7.9	35	.55	14.0	0.055	1.4	10.0	SPR	CG	N
0.765	19.43	11712	3.09	78.6	.553	14.0	79	14	.63	16	50	222	1.17	29.6	0.106	2.7	10.0	SPR	C	Z
0.765	19.43	10731	3.31	84.1	.669	17.0		1.2 .20	2.4	60	2.8	12	.95	24.1	0.048	1.2	19.8	SPR	CG	Z
0.765	19.43	11916	3.53	89.7	.555	14.1	34	6.0	1.3	33	45	200	1.86	47.3	0.105	2.7	17.8	SST	CG	N
0.765	19.43	3171	3.56	90.5	.635	16.1		6.4 1.1	2.0	52	13	58	.89	22.7	0.065	1.7	13.8	SPR	CG	Z
0.765	19.43	3929	3.75	95.3	.661	16.8		2.6 .46	2.5	65	6.7	30	.73	18.5	0.052	1.3	13.0	SPR	C	Z
0.765	19.43	10322	4.13	104.8	.425	10.8	326	57	.54	14	176	782	3.32	84.2	0.170	4.3	19.5	SPR	CG	Z
0.765	19.43	S-3220	4.50	114.3	.639	16.2		3.4 .60	3.3	83	11	50	1.20	30.4	0.063	1.6	19.0	SST	CG	N
0.765	19.43	S-457	4.63	117.5	.621	15.8		6.5 1.1	2.4	61	16	70	1.26	32.0	0.072	1.8	17.5	SST	CG	N
0.765	19.43	11859	4.69	119.0	.579	14.7	18	3.1	1.9	49	34	151	2.05	52.0	0.093	2.4	22.0	SPR	CG	N
0.765	19.43	3291	5.50	139.7	.601	15.3	15	2.6	1.7	43	24	109	1.31	33.3	0.082	2.1	16.0	SPR	CG	Z
0.765	19.43	12185	7.75	196.9	.549	13.9	22	3.8	2.4	62	53	234	3.67	93.3	0.108	2.7	34.0	SPR	CG	N
0.765	19.43	11828	8.00	203.2	.643	16.3		2.2 .38	4.7	118	10	45	1.54	39.1	0.061	1.5	25.3	SST	CG	N
0.765	19.43	3030	8.00	203.2	.615	15.6		6.2 1.1	3.1	78	19	84	1.84	46.7	0.075	1.9	24.5	SPR	CG	GI
0.781	19.84	Q-63	.44	11.1	.651	16.5	61	11	.20	5.0	12	53	.20	5.0	0.065	1.7	3.00	SST	CG	N
0.781	19.84	PP-8	.50	12.7	.541	13.7	1032	181	.07	1.7	68	302	.36	9.1	0.120	3.0	3.00	SPR	CG	N
0.781	19.84	2619	.69	17.4	.687	17.4		10 1.8	.51	13	5.2	23	.18	4.5	0.047	1.2	3.75	HD	CG	Z
0.781	19.84	12319	.72	18.2	.581	14.8	152	27	.22	5.5	33	147	.50	12.7	0.100	2.5	5.00	SPR	CG	Z
0.781	19.84	V-64	.75	19.1	.667	16.9	14	2.4	.49	13	6.9	31	.26	6.5	0.057	1.4	4.50	SST	CG	N
0.781	19.84	S-29	.75	19.1	.541	13.7	458	80	.14	3.4	62	275	.48	12.2	0.120	3.0	4.00	SST	CG	N
0.781	19.84	3743	.88	22.2	.699	17.8		3.3 .59	.63	16	2.1	9.3	.25	6.2	0.041	1.0	5.00	SPR	C	Z
0.781	19.84	11379	.88	22.2	.691	17.6		6.6 1.1	.65	17	4.3	19	.23	5.7	0.045	1.1	4.00	SST	C	N
0.781	19.84	LL-50	.88	22.2	.681	17.3	12	2.0	.51	13										



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.781	19.84	3127	1.63	41.3	.641	16.3	19	3.4	.78	20	15	67	.49	12.4	0.070	1.8	7.00	SPR	CG	Z
0.781	19.84	64	1.63	41.3	.541	13.7	147	26	.46	12	68	302	1.08	27.4	0.120	3.0	9.00	HD	CG	Z
0.781	19.84	BB-55	1.63	41.3	.461	11.7	582	102	.22	5.7	130	577	1.28	32.5	0.162	4.1	8.00	SST	CG	N
0.781	19.84	S-300	1.88	47.6	.637	16.2	16	2.8	.98	25	15	68	.58	14.6	0.072	1.8	8.00	SST	CG	N
0.781	19.84	11950	2.00	50.8	.461	11.7	605	106	.24	6.1	146	650	1.36	34.5	0.160	4.1	8.50	SPR	CG	Z
0.781	19.84	387	2.25	57.2	.541	13.7	103	18	.66	17	68	302	1.44	36.6	0.120	3.0	12.0	HD	CG	Z
0.781	19.84	S-1198	2.38	60.3	.657	16.7	9.0	1.6	1.2	29	10	46	.47	11.8	0.062	1.6	7.50	SST	CG	N
0.781	19.84	S-1273	2.44	61.9	.673	17.1	4.6	.81	1.5	38	6.9	31	.43	11.0	0.054	1.4	8.00	SST	CG	N
0.781	19.84	4204	2.50	63.5	.699	17.8	2.0	.35	1.7	44	3.5	15	.29	7.3	0.041	1.0	7.00	SPR	CG	Z
0.781	19.84	4139	2.63	66.7	.515	13.1	154	27	.58	15	89	394	1.70	43.1	0.133	3.4	12.8	SPR	CG	Z
0.781	19.84	3361	2.69	68.2	.511	13.0	161	28	.57	15	92	411	1.76	44.6	0.135	3.4	13.0	SPR	CG	Z
0.781	19.84	3760	2.75	69.9	.691	17.6	2.6	.45	1.8	45	4.6	20	.39	10.0	0.045	1.1	7.75	SPR	C	Z
0.781	19.84	12322	2.78	70.6	.609	15.5	20	3.4	1.4	36	28	123	1.20	30.6	0.086	2.2	14.0	SPR	CG	GI
0.781	19.84	12275	2.84	72.2	.587	14.9	57	9.9	.66	17	38	168	.87	22.2	0.097	2.5	9.00	SPR	CG	Z
0.781	19.84	3484	2.88	73.0	.531	13.5	131	23	.58	15	76	339	1.44	36.5	0.125	3.2	11.5	HD	CG	Z
0.781	19.84	YY-38	3.38	85.7	.691	17.6	1.2	.20	2.7	70	3.2	14	.63	16.0	0.045	1.1	13.0	SST	C	N
0.781	19.84	10818	3.50	88.9	.731	18.6	.10	.02	3.1	79	.32	1.4	.39	10.0	0.025	0.6	14.8	MW	C	N
0.781	19.84	3293	3.50	88.9	.661	16.8	4.1	.73	2.4	62	10	45	.90	22.9	0.060	1.5	14.0	SPR	C	Z
0.781	19.84	3305	3.50	88.9	.597	15.2	29	5.0	1.1	29	32	144	1.20	30.4	0.092	2.3	13.0	SPR	CG	Z
0.781	19.84	3224	3.56	90.5	.585	14.9	28	4.9	1.4	36	39	173	1.67	42.3	0.098	2.5	17.0	SPR	CG	Z
0.781	19.84	3461	3.63	92.1	.657	16.7	5.7	1.0	1.9	49	11	49	.74	18.9	0.062	1.6	12.0	HD	CG	Z
0.781	19.84	4217	4.00	101.6	.689	17.5	1.5	.27	3.2	80	4.9	22	.62	15.8	0.046	1.2	12.5	SPR	C	Z
0.781	19.84	11533	4.00	101.6	.657	16.7	2.8	.47	2.5	63	6.6	29	1.52	38.6	0.062	1.6	23.5	SPR	CG	Z
0.781	19.84	B7-53	4.19	106.4	.637	16.2	6.1	1.1	2.5	64	15	68	1.28	32.5	0.072	1.8	17.8	SST	CG	N
0.781	19.84	12037	5.56	141.3	.589	15.0	17	3.0	2.1	54	37	163	2.30	58.5	0.096	2.4	24.0	SPR	CG	Z
0.785	19.94	12787	1.31	33.3	.709	18.0	1.9	.34	1.1	27	2.0	9.0	.26	6.5	0.038	1.0	5.75	MW	C	N
0.796	20.22	2740	.66	16.7	.652	16.6	34	5.9	.30	7.5	10	45	.36	9.1	0.072	1.8	5.00	MW	CG	Z
0.796	20.22	1647	.75	19.1	.688	17.5	9.0	1.6	.41	10	3.7	16	.34	8.7	0.054	1.4	5.33	SPR	C	Z
0.796	20.22	11810	.84	21.4	.674	17.1	17	2.9	.54	14	9.0	40	.31	7.7	0.061	1.5	5.00	SPR	CG	Z
0.796	20.22	PP-88	.97	24.6	.536	13.6	463	81	.18	4.5	82	363	.65	16.5	0.130	3.3	5.00	SPR	CG	N
0.796	20.22	B11-38	1.00	25.4	.708	18.0	3.6	.63	.76	19	2.7	12	.24	6.1	0.044	1.1	5.50	SPR	CG	N
0.796	20.22	MM-99	1.03	26.2	.536	13.6	352	62	.21	5.3	73	327	.72	18.2	0.130	3.3	5.50	SST	CG	N
0.796	20.22	A11-32	1.06	27.0	.612	15.5	87	15	.34	8.6	29	131	.46	11.7	0.092	2.3	5.00	SST	CG	N
0.796	20.22	S-491	1.06	27.0	.546	13.9	294	52	.23	5.9	68	304	.69	17.5	0.125	3.2	5.50	SST	CG	N
0.796	20.22	S-804	1.19	30.2	.688	17.5	6.5	1.1	.86	22	5.6	25	.32	8.2	0.054	1.4	6.00	SST	CG	N
0.796	20.22	2857	1.22	31.0	.666	16.9	16	2.9	.83	21	14	61	.39	9.9	0.065	1.7	6.00	MW	CG	Z
0.796	20.22	Y-28	1.28	32.5	.596	15.1	90	16	.45	11	41	180	.68	17.1	0.100	2.5	6.75	SPR	CG	Z
0.796	20.22	S-870	1.31	33.3	.702	17.8	5.3	.92	.91	23	4.8	21	.22	5.7	0.047	1.2	4.75	SST	CG	N
0.796	20.22	3759	1.31	33.3	.616	15.6	60	10	.50	13	30	132	.68	17.1	0.090	2.3	6.50	SPR	C	Z
0.796	20.22	S-441	1.31	33.3	.614	15.6	55	9.7	.51	13	29	127	.59	15.0	0.091	2.3	6.50	SST	CG	N
0.796	20.22	3116	1.34	34.1	.526	13.4	367	64	.25	6.3	91	404	.88	22.3	0.135	3.4	6.50	SPR	CG	Z
0.796	20.22	B8-51	1.38	34.9	.456	11.6	979	171	.17	4.4	170	758	1.19	30.2	0.170	4.3	7.00	SPR	CG	Z
0.796	20.22	S-1142	1.50	38.1	.716	18.2	1.3	.24	1.2	29	1.6	6.9	.34	8.6	0.040	1.0	7.50	SST	C	N
0.796	20.22	S-1207	1.50	38.1	.652	16.6	22	3.9	.68	17	15	67	.43	11.0	0.072	1.8	6.00	SST	CG	N
0.796	20.22	MM-51	1.50	38.1	.596	15.1	58	10	.65	16	38	167	.85	21.6	0.100	2.5	8.50	SST	CG	N
0.796	20.22	A13-66	1.50	38.1	.586	14.9	94	16	.46	12	43	193	.74	18.7	0.105	2.7	7.00	SST	CG	N
0.796	20.22	10668	1.50	38.1	.552	14.0	181	32	.39	9.8	70	311	.95	24.0	0.122	3.1	7.75	SPR	CG	Z
0.796	20.22	S-3156	1.56	39.7	.672	17.1	5.8	1.0	.94	24	5.5	24	.62	15.7	0.062	1.6	10.0	SST	CG	N
0.796	20.22	BB-28	1.63	41.3	.676	17.2	9.2	1.6	1.0	26	9.3	41	.39	9.9	0.060	1.5	6.50	SST	CG	N
0.796	20.22	S-234	1.69	42.8	.688	17.5	5.3	.93	1.3	33	6.8	30	.38	9.6	0.054	1.4	7.00	SST	CG	N
0.796	20.22	S-1173	1.75	44.5	.586	14.9	46	8.1	.49	12	23	100	1.26	32.0	0.105	2.7	12.0	SST	CG	N
0.796	20.22	B8-52	1.91	48.4	.680	17.3	7.0	1.2	1.3	32	8.9	40	.45	11.4	0.058	1.5	7.75	SPR	CG	N
0.796	20.22	10628	2.00	50.8	.672	17.1	5.7	.99	1.3	33	7.3	32	.71	18.1	0.062	1.6	11.5	SPR	CG	Z
0.796	20.22	S-1029	2.00	50.8	.668	17.0	4.5	.78	1.1	28	4.9	22	.90	22.8	0.064	1.6	14.0	SST	CG	N
0.796	20.22	LL-48	2.00	50.8	.656	16.7	6.7	1.2	1.0	26	6.8	30	.98	24.9	0.070	1.8	14.0	SST	CG	N
0.796	20.22	2798	2.00	50.8	.612	15.5	42	7.4	.75	19	32	141	.83	21.0	0.092	2.3	9.00	SPR	CG	Z
0.796	20.22	10052	2.00	50.8	.484	12.3	481	84	.28	7.1	134									




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.796	20.22	10848	8.25	209.6	.676	17.2	2.3	.41	4.2	107	9.9	44	1.38	35.1	0.060	1.5	22.0	SPR	C	GI
0.796	20.22	3054	9.00	228.6	.672	17.1	3.0	.52	3.6	93	11	48	1.30	33.1	0.062	1.6	20.0	SPR	C	Z
0.796	20.22	S-76	11.4	288.9	.466	11.8	88	15	1.6	40	139	619	7.26	184.4	0.165	4.2	44.0	SST	CG	N
0.812	20.62	DD-6	.38	9.5	.762	19.4	.33	.06	.21	5.4	.07	.31	.16	4.1	0.025	0.6	5.50	MW	C	Z
0.812	20.62	BB-77	.44	11.1	.698	17.7	18	3.1	.21	5.3	3.7	16	.23	5.8	0.057	1.4	4.00	SPR	CG	N
0.812	20.62	2856	.47	11.9	.704	17.9	11	2.0	.23	5.7	2.5	11	.24	6.2	0.054	1.4	4.50	HD	CG	Z
0.812	20.62	FF-36	.50	12.7	.692	17.6	18	3.1	.17	4.3	3.0	13	.33	8.4	0.060	1.5	4.50	SPR	C	N
0.812	20.62	S-939	.69	17.4	.668	17.0	56	9.9	.26	6.7	15	66	.25	6.4	0.072	1.8	3.50	SST	CG	N
0.812	20.62	3356	.69	17.4	.642	16.3	98	17	.26	6.7	26	114	.34	8.6	0.085	2.2	4.00	SPR	CG	Z
0.812	20.62	DD-84	.72	18.2	.722	18.3	3.2	.57	.47	12	1.5	6.8	.25	6.3	0.045	1.1	5.50	SST	CG	N
0.812	20.62	II-7	.78	19.8	.692	17.6	9.7	1.7	.42	11	4.1	18	.36	9.1	0.060	1.5	6.00	SST	CG	N
0.812	20.62	11432	.81	20.6	.662	16.8	28	5.0	.36	9.2	10	46	.45	11.4	0.075	1.9	6.00	SPR	CG	Z
0.812	20.62	H-21	.81	20.6	.602	15.3	195	34	.22	5.5	43	189	.45	11.3	0.105	2.7	4.25	SST	CG	N
0.812	20.62	12639	.88	22.2	.520	13.2	1474	258	.07	1.7	101	448	.51	13.0	0.146	3.7	3.50	SST	C	N
0.812	20.62	S-123	1.00	25.4	.704	17.9	11	1.9	.61	16	6.7	30	.23	5.8	0.054	1.4	4.25	SST	CG	N
0.812	20.62	10340	1.00	25.4	.686	17.4	18	3.1	.62	16	11	50	.38	9.6	0.063	1.6	5.00	SPR	C	Z
0.812	20.62	FF-68	1.00	25.4	.532	13.5	497	87	.18	4.6	89	397	.74	18.7	0.140	3.6	5.25	SST	CG	N
0.812	20.62	3038	1.03	26.2	.632	16.1	61	11	.48	12	29	129	.55	14.0	0.090	2.3	6.00	SPR	CG	GI
0.812	20.62	B10-52	1.13	28.6	.648	16.5	42	7.3	.55	14	23	103	.49	12.5	0.082	2.1	6.00	SPR	CG	Z
0.812	20.62	4160	1.19	30.2	.496	12.6	801	140	.17	4.3	137	607	.95	24.1	0.158	4.0	6.00	SPR	CG	Z
0.812	20.62	S-1609	1.22	31.0	.602	15.3	110	19	.39	9.9	43	189	.63	16.0	0.105	2.7	6.00	SST	CG	N
0.812	20.62	1918	1.22	31.0	.504	12.8	710	124	.18	4.5	127	565	.92	23.5	0.154	3.9	6.00	SPR	CG	Z
0.812	20.62	KK-6	1.25	31.8	.592	15.0	122	21	.42	11	51	226	.77	19.6	0.110	2.8	7.00	SPR	CG	N
0.812	20.62	S-933	1.28	32.5	.686	17.4	12	2.1	.84	21	10	45	.44	11.2	0.063	1.6	6.00	SST	C	N
0.812	20.62	K-48	1.38	34.9	.528	13.4	389	68	.27	6.8	103	460	.99	25.2	0.142	3.6	7.00	SPR	CG	Z
0.812	20.62	2680	1.38	34.9	.500	12.7	670	117	.28	7.0	184	821	1.01	25.8	0.156	4.0	6.50	MW	CG	Z
0.812	20.62	63	1.38	34.9	.488	12.4	721	126	.20	5.2	147	652	1.13	28.8	0.162	4.1	7.00	HD	CG	Z
0.812	20.62	S-25	1.50	38.1	.758	19.3	.34	.06	1.3	33	.45	2.0	.19	4.8	0.027	0.7	6.00	SST	C	N
0.812	20.62	10601	1.50	38.1	.728	18.5	1.4	.25	1.1	27	1.5	6.7	.42	10.7	0.042	1.1	9.00	SPR	C	Z
0.812	20.62	S-366	1.50	38.1	.718	18.2	3.4	.60	1.2	31	4.1	18	.28	7.2	0.047	1.2	6.00	SST	CG	N
0.812	20.62	12554	1.50	38.1	.652	16.6	26	4.6	.77	20	20	90	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.812	20.62	S-3207	1.53	38.9	.602	15.3	88	15	.48	12	43	189	.74	18.7	0.105	2.7	7.00	SST	CG	N
0.812	20.62	10788	1.63	41.3	.688	17.5	9.9	1.7	1.0	26	10	45	.47	11.8	0.062	1.6	6.50	SST	C	N
0.812	20.62	3960	1.63	41.3	.572	14.5	138	24	.47	12	65	291	1.02	25.9	0.120	3.0	8.50	SPR	CG	Z
0.812	20.62	S-799	1.66	42.1	.716	18.2	3.8	.66	1.3	34	5.0	22	.29	7.3	0.048	1.2	6.00	SST	CG	N
0.812	20.62	3801	1.69	42.8	.602	15.3	76	13	.60	15	46	204	.89	22.7	0.105	2.7	8.50	SPR	CG	GI
0.812	20.62	2645	1.75	44.5	.688	17.5	4.2	.73	.82	21	3.4	15	.93	23.6	0.062	1.6	14.0	HD	C	Z
0.812	20.62	12605	1.75	44.5	.652	16.6	27	4.8	1.1	27	29	130	.68	17.3	0.080	2.0	7.50	MW	C	N
0.812	20.62	3079	1.75	44.5	.572	14.5	124	22	.53	13	65	291	1.11	28.2	0.120	3.0	9.25	SPR	CG	Z
0.812	20.62	3354	1.75	44.5	.572	14.5	129	23	.51	13	65	291	1.20	30.5	0.120	3.0	9.00	SPR	C	Z
0.812	20.62	3139	1.78	45.2	.518	13.2	380	67	.30	7.6	114	507	1.18	29.9	0.147	3.7	8.00	SPR	CG	Z
0.812	20.62	12490	1.81	46.0	.706	17.9	3.8	.66	1.3	34	5.0	22	.48	12.1	0.053	1.3	8.00	SST	C	N
0.812	20.62	65	1.88	47.6	.572	14.5	116	20	.56	14	65	291	1.17	29.7	0.120	3.0	9.75	HD	CG	Z
0.812	20.62	2974	2.00	50.8	.730	18.5	1.1	.19	1.5	39	1.7	7.6	.45	11.5	0.041	1.0	10.0	SPR	C	Z
0.812	20.62	3282	2.00	50.8	.688	17.5	5.0	.88	1.3	32	6.3	28	.74	18.9	0.062	1.6	12.0	HD	CG	Z
0.812	20.62	12157	2.13	54.0	.650	16.5	26	4.6	.85	21	22	99	.65	16.5	0.081	2.1	8.00	SPR	CG	GI
0.812	20.62	S-1215	2.13	54.0	.612	15.5	35	6.1	.93	23	32	142	1.20	30.5	0.100	2.5	12.0	SST	CG	N
0.812	20.62	11959	2.16	54.8	.744	18.9	.52	.09	1.8	46	.94	4.2	.34	8.6	0.034	0.9	9.00	SST	C	N
0.812	20.62	3945	2.19	55.6	.704	17.9	3.1	.55	1.5	39	4.8	21	.65	16.5	0.054	1.4	11.0	SPR	C	Z
0.812	20.62	B8-35	2.25	57.2	.708	18.0	2.7	.46	1.7	44	4.6	20	.52	13.2	0.052	1.3	10.0	SST	CG	N
0.812	20.62	69	2.25	57.2	.602	15.3	55	9.6	.84	21	46	204	1.26	32.0	0.105	2.7	11.0	HD	CG	Z
0.812	20.62	70	2.25	57.2	.572	14.5	112	20	.58	15	65	291	1.32	33.5	0.120	3.0	10.0	HD	C	Z
0.812	20.62	11217	2.25	57.2	.562	14.3	117	20	.63	16	74	328	1.41	35.7	0.125	3.2	11.3	HD	CG	Z
0.812	20.62	12145	2.50	63.5	.684	17.4	5.2	.92	1.7	42	8.7	39	.83	21.1	0.064	1.6	13.0	SPR	CG	Z
0.812	20.62	S-1612	2.50	63.5	.682	17.3	4.6	.80	1.5	39	6.9	31	.98	24.8	0.065	1.7	14.0	SST	C	N
0.812	20.62	12061	2.50	63.5	.652	16.6	14	2.4	1.5	37	20	89	1.04	26.4	0.080	2.0	13.0	SPR	CG	Z
0.812	20.62	11188	2.50	63.5	.642	16.3	19	3.4	1.3	32	24	107	1.02	25.9	0.085	2.2	11.0	SST	C	N
0.812	20.62	S-3090	2.50	63.5	.612	15														



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.812	20.62	2738	5.50	139.7	.592	15.0	30	5.2	1.7	44	51	226	2.48	62.9	0.110	2.8	22.5	SPR	CG	Z
0.812	20.62	10214	7.00	177.8	.602	15.3	22	3.8	2.1	53	46	204	2.57	65.4	0.105	2.7	24.5	SPR	CG	Z
0.812	20.62	2997	9.19	233.4	.516	13.1	54	9.4	2.2	55	116	517	6.81	172.9	0.148	3.8	46.0	SPR	CG	Z
0.812	20.62	12741	10.0	254.0	.558	14.2	31	5.4	2.5	64	77	343	5.21	132.3	0.127	3.2	40.0	SPR	C	N
0.812	20.62	4244	15.5	393.7	.602	15.3	11	1.9	4.1	105	46	204	4.88	124.0	0.105	2.7	46.5	SPR	CG	Z
0.822	20.88	B2-66	2.63	66.7	.550	14.0	160	28	.65	16	105	466	1.70	43.2	0.136	3.5	11.5	OT	C	N
0.828	21.03	11483	.50	12.7	.728	18.5	19	3.3	.29	7.4	5.5	25	.20	5.1	0.050	1.3	3.00	SPR	CG	Z
0.828	21.03	B14-67	.50	12.7	.672	17.1	126	22	.16	3.9	20	87	.23	5.9	0.078	2.0	3.00	SPR	CG	Z
0.828	21.03	KK-62	.50	12.7	.588	14.9	745	130	.08	2.0	59	261	.36	9.1	0.120	3.0	3.00	SST	CG	N
0.828	21.03	S-349	.72	18.2	.642	16.3	320	56	.09	2.3	29	130	.26	6.5	0.093	2.4	2.75	SST	CG	N
0.828	21.03	S-416	.78	19.8	.704	17.9	10	1.8	.41	10	4.3	19	.37	9.4	0.062	1.6	6.00	SST	CG	N
0.828	21.03	S-1111	.81	20.6	.764	19.4	1.0	.18	.64	16	.66	2.9	.18	4.5	0.032	0.8	4.50	SST	C	N
0.828	21.03	3872	.81	20.6	.732	18.6	11	1.9	.49	12	5.2	23	.22	5.5	0.048	1.2	3.50	SPR	C	Z
0.828	21.03	11361	.81	20.6	.668	17.0	71	12	.28	7.0	20	88	.30	7.6	0.080	2.0	3.75	SST	CG	N
0.828	21.03	11227	.84	21.4	.474	12.0	2922	512	.06	1.6	185	822	.66	16.9	0.177	4.5	3.75	SPR	CG	Z
0.828	21.03	CC-68	.88	22.2	.648	16.5	42	7.3	.25	6.2	10	45	.63	16.0	0.090	2.3	7.00	SST	CG	N
0.828	21.03	2958	.91	23.0	.734	18.6	3.7	.64	.62	16	2.3	10	.28	7.2	0.047	1.2	6.00	SPR	CG	Z
0.828	21.03	12430	.94	23.8	.742	18.8	9.0	1.6	.39	10	3.5	16	.17	4.4	0.043	1.1	3.00	SST	C	N
0.828	21.03	S-3206	.94	23.8	.732	18.6	8.1	1.4	.60	15	4.9	22	.18	4.6	0.048	1.2	3.75	SST	CG	N
0.828	21.03	12315	1.00	25.4	.764	19.4	.75	.13	.81	21	.60	2.7	.19	4.9	0.032	0.8	6.00	SPR	CG	Z
0.828	21.03	KK-58	1.00	25.4	.728	18.5	9.5	1.7	.58	15	5.5	25	.20	5.1	0.050	1.3	4.00	SPR	CG	Z
0.828	21.03	4333	1.00	25.4	.704	17.9	16	2.8	.63	16	9.9	44	.37	9.4	0.062	1.6	5.00	SPR	C	N
0.828	21.03	10792	1.00	25.4	.646	16.4	55	9.6	.45	12	25	110	.55	13.9	0.091	2.3	6.00	SST	CG	N
0.828	21.03	KK-97	1.00	25.4	.608	15.4	112	20	.29	7.2	32	142	.72	18.2	0.110	2.8	6.50	SST	CG	N
0.828	21.03	11478	1.03	26.2	.728	18.5	9.5	1.7	.58	15	5.5	25	.25	6.4	0.050	1.3	4.00	SPR	CG	Z
0.828	21.03	3852	1.06	27.0	.732	18.6	4.3	.75	.74	19	3.2	14	.32	8.2	0.048	1.2	5.75	SPR	C	Z
0.828	21.03	11696	1.06	27.0	.648	16.5	59	10	.49	12	29	128	.54	13.7	0.090	2.3	6.00	SPR	CG	GI
0.828	21.03	12176	1.22	31.0	.516	13.1	701	123	.18	4.7	130	576	.94	23.8	0.156	4.0	6.00	SPR	CG	Z
0.828	21.03	10702	1.38	34.9	.700	17.8	18	3.2	.64	16	12	51	.32	8.1	0.064	1.6	5.00	SPR	CG	Z
0.828	21.03	A13-64	1.38	34.9	.686	17.4	28	4.9	.53	13	15	66	.36	9.0	0.071	1.8	5.00	SPR	CG	GI
0.828	21.03	10944	1.50	38.1	.708	18.0	10	1.8	.92	23	9.5	42	.36	9.1	0.060	1.5	6.00	SPR	CG	Z
0.828	21.03	S-3163	1.50	38.1	.708	18.0	29	5.1	.30	7.7	8.9	40	.48	12.2	0.060	1.5	6.00	SST	CG	N
0.828	21.03	3424	1.50	38.1	.418	10.6	2100	368	.07	1.7	136	607	1.44	36.4	0.205	5.2	7.00	SPR	CG	Z
0.828	21.03	S-292	1.63	41.3	.644	16.4	35	6.1	.82	21	28	126	.78	19.9	0.092	2.3	8.50	SST	CG	N
0.828	21.03	S-1080	1.75	44.5	.724	18.4	4.3	.76	1.3	34	5.8	26	.39	9.9	0.052	1.3	6.50	SST	C	N
0.828	21.03	11768	1.75	44.5	.648	16.5	39	6.8	.73	19	29	128	.72	18.3	0.090	2.3	8.00	SPR	CG	Z
0.828	21.03	KK-35	1.81	46.0	.608	15.4	53	9.3	.55	14	29	129	1.27	32.1	0.110	2.8	11.5	SST	CG	N
0.828	21.03	TT-59	1.88	47.6	.668	17.0	24	4.3	.81	21	20	88	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.828	21.03	NN-8	1.88	47.6	.588	14.9	115	20	.51	13	59	261	1.02	25.9	0.120	3.0	8.50	SST	CG	N
0.828	21.03	10527	1.91	48.4	.532	13.5	366	64	.31	7.9	114	509	1.18	30.1	0.148	3.8	8.00	SPR	CG	N
0.828	21.03	12211	1.94	49.2	.708	18.0	8.2	1.4	1.2	29	9.5	42	.42	10.7	0.060	1.5	7.00	SPR	CG	Z
0.828	21.03	S-339	2.00	50.8	.578	14.7	117	21	.56	14	66	294	1.19	30.2	0.125	3.2	9.50	SST	CG	N
0.828	21.03	3226	2.09	53.2	.638	16.2	42	7.4	.79	20	34	150	.95	24.1	0.095	2.4	9.00	SPR	C	Z
0.828	21.03	S-361	2.13	54.0	.668	17.0	17	3.1	1.1	29	20	88	.72	18.3	0.080	2.0	9.00	SST	CG	N
0.828	21.03	10591	2.13	54.0	.668	17.0	23	4.1	.90	23	21	94	.72	18.3	0.080	2.0	8.00	SPR	C	Z
0.828	21.03	11987	2.19	55.6	.716	18.2	2.9	.51	1.5	38	4.4	19	.70	17.8	0.056	1.4	12.5	SPR	CG	GI
0.828	21.03	DD-80	2.50	63.5	.668	17.0	15	2.7	1.4	35	21	94	.90	22.9	0.080	2.0	11.3	SPR	CG	GI
0.828	21.03	11354	2.50	63.5	.668	17.0	14	2.4	1.4	36	20	88	.96	24.4	0.080	2.0	11.0	SST	C	N
0.828	21.03	1903	2.50	63.5	.646	16.4	25	4.4	1.2	30	30	132	1.07	27.2	0.091	2.3	11.8	SPR	CG	Z
0.828	21.03	11258	2.50	63.5	.578	14.7	101	18	.72	18	72	322	1.50	38.1	0.125	3.2	12.0	SPR	CG	Z
0.828	21.03	11933	2.63	66.7	.738	18.7	1.8	.31	2.2	56	3.9	17	.41	10.3	0.045	1.1	9.00	SPR	CG	Z
0.828	21.03	10806	2.63	66.7	.658	16.7	18	3.2	1.3	33	24	105	1.02	25.9	0.085	2.2	11.0	SST	C	N
0.828	21.03	S-287	2.75	69.9	.742	18.8	.88	.15	2.2	57	2.0	8.8	.52	13.1	0.043	1.1	12.0	SST	CG	N
0.828	21.03	S-3038	2.88	73.0	.454	11.5	553	97	.32	8.1	177	788	2.34	59.4	0.187	4.7	12.5	SST	CG	N
0.828	21.03	S-3202	3.00	76.2	.762	19.4	.25	.04	2.5	64	.64	2.8	.46	11.7	0.033	0.8	14.0	SST	CG	N
0.828	21.03	S-63	3.00	76.2	.758	19.3	.31	.05	2.5	64	.79	3.5	.49	12.4	0.035	0.9	14.0	SST	CG	N
0.828	21.03	S-72	3.00	76.2	.618	15.7	50	8.8	.83	21	42	186	1.							



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.843	21.41	11530	.69	17.4	.575	14.6	743	130	.05	1.3	38	167	.64	16.2	0.134	3.4	3.75	SPR	CG	Z
0.843	21.41	4310	.69	17.4	.573	14.6	1076	188	.08	2.0	86	385	.44	11.1	0.135	3.4	3.25	SPR	CG	Z
0.843	21.41	S-371	.75	19.1	.657	16.7	111	19	.26	6.6	29	128	.37	9.4	0.093	2.4	4.00	SST	CG	N
0.843	21.41	XX-54	.81	20.6	.683	17.3	77	13	.25	6.4	19	87	.28	7.1	0.080	2.0	3.50	SST	CG	N
0.843	21.41	S-226	.91	23.0	.665	16.9	37	6.4	.28	7.2	10	46	.62	15.8	0.089	2.3	7.00	SST	CG	N
0.843	21.41	PP-48	1.00	25.4	.783	19.9	.96	.17	.88	22	.85	3.8	.12	3.0	0.030	0.8	4.00	SST	CG	N
0.843	21.41	S-150	1.00	25.4	.749	19.0	4.0	.71	.72	18	2.9	13	.28	7.2	0.047	1.2	5.00	SST	C	N
0.843	21.41	S-1155	1.00	25.4	.719	18.3	19	3.4	.50	13	9.7	43	.25	6.3	0.062	1.6	4.00	SST	CG	N
0.843	21.41	10028	1.00	25.4	.703	17.9	37	6.5	.37	9.5	14	62	.28	7.1	0.070	1.8	4.00	SPR	CG	Z
0.843	21.41	S-255	1.00	25.4	.693	17.6	26	4.6	.60	15	16	70	.40	10.2	0.075	1.9	5.33	SST	CG	N
0.843	21.41	S-1627	1.00	25.4	.673	17.1	56	9.7	.42	11	23	103	.49	12.4	0.085	2.2	4.75	SST	C	N
0.843	21.41	12668	1.00	25.4	.659	16.7	81	14	.52	13	42	187	.46	11.7	0.092	2.3	5.00	MW	CG	N
0.843	21.41	12674	1.00	25.4	.659	16.7	108	19	.39	9.9	42	187	.39	9.9	0.092	2.3	4.25	MW	CG	N
0.843	21.41	B15-22	1.03	26.2	.723	18.4	17	3.0	.51	13	8.8	39	.24	6.1	0.060	1.5	4.00	SST	CG	N
0.843	21.41	B6-47	1.06	27.0	.723	18.4	19	3.4	.48	12	9.3	42	.30	7.6	0.060	1.5	4.00	SPR	C	N
0.843	21.41	MM-56	1.09	27.8	.723	18.4	9.1	1.6	.72	18	6.6	29	.38	9.5	0.060	1.5	6.25	SPR	CG	N
0.843	21.41	QQ-59	1.13	28.6	.699	17.8	18	3.2	.69	18	13	56	.43	11.0	0.072	1.8	6.00	SST	CG	N
0.843	21.41	11139	1.19	30.2	.661	16.8	77	14	.38	9.6	29	130	.55	13.9	0.091	2.3	5.00	SPR	C	Z
0.843	21.41	M-23	1.25	31.8	.775	19.7	1.2	.21	1.0	27	1.3	5.6	.20	5.2	0.034	0.9	5.00	SPR	C	N
0.843	21.41	S-882	1.25	31.8	.713	18.1	16	2.9	.68	17	11	50	.32	8.0	0.065	1.7	5.00	SST	CG	N
0.843	21.41	K-63	1.25	31.8	.707	18.0	17	2.9	.82	21	14	60	.41	10.4	0.068	1.7	6.00	SPR	CG	GI
0.843	21.41	3095	1.25	31.8	.693	17.6	27	4.7	.64	16	17	76	.43	11.0	0.075	1.9	5.75	SPR	CG	Z
0.843	21.41	2892	1.28	32.5	.683	17.3	27	4.8	.73	19	20	88	.55	14.0	0.080	2.0	7.00	SPR	CG	Z
0.843	21.41	MM-12	1.28	32.5	.663	16.8	44	7.6	.60	15	26	116	.59	14.9	0.090	2.3	6.50	SST	CG	N
0.843	21.41	S-77	1.38	34.9	.761	19.3	2.1	.37	1.1	28	2.4	10	.26	6.5	0.041	1.0	5.25	SST	C	N
0.843	21.41	11995	1.38	34.9	.715	18.2	7.3	1.3	.80	20	5.8	26	.58	14.6	0.064	1.6	9.00	SPR	CG	Z
0.843	21.41	S-807	1.41	35.7	.683	17.3	29	5.0	.67	17	19	87	.48	12.2	0.080	2.0	6.00	SST	CG	N
0.843	21.41	11784	1.41	35.7	.647	16.4	71	12	.51	13	36	161	.64	16.2	0.098	2.5	6.50	SPR	CG	N
0.843	21.41	10821	1.41	35.7	.583	14.8	227	40	.34	8.7	78	345	.91	23.1	0.130	3.3	7.00	SPR	CG	Z
0.843	21.41	3168	1.47	37.3	.735	18.7	5.0	.87	1.1	28	5.4	24	.38	9.6	0.054	1.4	7.00	SPR	CG	Z
0.843	21.41	1649	1.50	38.1	.731	18.6	7.3	1.3	1.0	27	7.6	34	.39	10.0	0.056	1.4	6.00	SPR	C	Z
0.843	21.41	3214	1.50	38.1	.715	18.2	17	3.0	.66	17	11	50	.38	9.8	0.064	1.6	5.00	SPR	CG	Z
0.843	21.41	B12-64	1.50	38.1	.713	18.1	12	2.1	.98	25	12	53	.49	12.4	0.065	1.7	6.50	SPR	C	N
0.843	21.41	12612	1.50	38.1	.683	17.3	33	5.8	.63	16	21	92	.48	12.2	0.080	2.0	6.00	SPR	CG	Z
0.843	21.41	S-54	1.50	38.1	.623	15.8	124	22	.36	9.2	45	199	.63	16.1	0.110	2.8	5.75	SST	CG	N
0.843	21.41	S-1483	1.56	39.7	.683	17.3	18	3.1	.88	22	16	70	.68	17.3	0.080	2.0	8.50	SST	CG	N
0.843	21.41	1775	1.59	40.5	.715	18.2	6.2	1.1	.94	24	5.8	26	.66	16.7	0.064	1.6	10.3	SPR	CG	Z
0.843	21.41	1569	1.63	41.3	.763	19.4	2.0	.36	1.4	35	2.8	12	.26	6.6	0.040	1.0	5.50	SPR	C	Z
0.843	21.41	S-1478	1.63	41.3	.727	18.5	5.8	1.0	1.2	31	7.1	32	.41	10.3	0.058	1.5	7.00	SST	CG	N
0.843	21.41	S-3001	1.63	41.3	.719	18.3	10	1.8	.94	24	9.7	43	.36	9.1	0.062	1.6	5.75	SST	CG	N
0.843	21.41	10703	1.75	44.5	.735	18.7	5.9	1.0	1.2	30	6.8	30	.39	10.0	0.054	1.4	6.25	SPR	C	Z
0.843	21.41	S-824	1.75	44.5	.683	17.3	14	2.5	.95	24	14	61	.80	20.3	0.080	2.0	10.0	SST	CG	N
0.843	21.41	B12-37	2.00	50.8	.661	16.8	39	6.8	.75	19	29	130	.82	20.8	0.091	2.3	8.00	SPR	C	N
0.843	21.41	12613	2.00	50.8	.643	16.3	58	10	.92	23	54	239	.90	22.9	0.100	2.5	8.00	MW	C	N
0.843	21.41	S-82	2.00	50.8	.603	15.3	110	19	.53	13	58	257	1.11	28.2	0.120	3.0	8.25	SST	C	N
0.843	21.41	JJ-54	2.00	50.8	.503	12.8	499	87	.29	7.4	145	643	1.53	38.9	0.170	4.3	9.00	SST	CG	N
0.843	21.41	MM-55	2.03	51.6	.603	15.3	93	16	.62	16	58	257	1.14	29.0	0.120	3.0	9.50	SST	CG	N
0.843	21.41	S-66	2.06	52.4	.603	15.3	112	20	.52	13	58	257	.99	25.1	0.120	3.0	8.25	SST	CG	N
0.843	21.41	11949	2.09	53.2	.517	13.1	409	72	.31	8.0	128	571	1.47	37.3	0.163	4.1	9.00	SST	CG	N
0.843	21.41	10239	2.19	55.6	.661	16.8	66	12	.44	11	29	130	.50	12.7	0.091	2.3	5.50	SPR	CG	Z
0.843	21.41	S-3258	2.25	57.2	.703	17.9	11	1.9	1.2	30	13	58	.56	14.2	0.070	1.8	8.00	SST	CG	N
0.843	21.41	11781	2.28	57.9	.525	13.3	364	64	.33	8.4	120	532	1.43	36.3	0.159	4.0	9.00	SST	CG	N
0.843	21.41	3501	2.44	61.9	.699	17.8	12	2.1	1.7	44	21	92	.72	18.3	0.072	1.8	9.00	MW	C	Z
0.843	21.41	11185	2.47	62.7	.633	16.1	62	11	.71	18	44	197	.95	24.0	0.105	2.7	9.00	HD	CG	Z
0.843	21.41	2842	2.50	63.5	.709	18.0	7.1	1.2	1.8	45	13	56	.72	18.3	0.067	1.7	10.8	HD	CG	Z
0.843	21.41	B10-9	2.50	63.5	.697	17.7	12	2.2	1.3	33	16	70	.68	17.2	0.073	1.9	9.25	SPR	CG	BO
0.843	21.41	3266	2.75	69.9	.633	16.1	51	9.0	.87	22	44	197	1.10	28.0	0.105	2.7	10.5	SPR	CG	Z
0.843	21.41	11902	2.81	71.4	.579	14.7	110	19	.73.											



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.850	21.59	72162S	.75	19.1	.716	18.2	29	5.1	.42	11	12	54	.25	6.4	0.067	1.7	3.75	SST	CG	N
0.850	21.59	72172	.75	19.1	.714	18.1	36	6.3	.50	13	18	79	.26	6.5	0.068	1.7	3.75	MW	CG	N
0.850	21.59	72172S	.75	19.1	.714	18.1	31	5.3	.41	11	13	56	.26	6.5	0.068	1.7	3.75	SST	CG	N
0.850	21.59	72210	.75	19.1	.690	17.5	67	12	.43	11	29	128	.31	7.9	0.080	2.0	3.88	MW	CG	N
0.850	21.59	72210S	.75	19.1	.690	17.5	57	9.9	.34	8.6	19	86	.31	7.9	0.080	2.0	3.88	SST	CG	N
0.850	21.59	72233	.75	19.1	.688	17.5	68	12	.43	11	29	128	.32	8.2	0.081	2.1	4.00	MW	CG	N
0.850	21.59	72233S	.75	19.1	.688	17.5	58	10	.35	8.8	20	89	.32	8.2	0.081	2.1	4.00	SST	CG	N
0.850	21.59	72246	.75	19.1	.680	17.3	84	15	.41	10	34	153	.34	8.6	0.085	2.2	4.00	MW	CG	N
0.850	21.59	72246S	.75	19.1	.680	17.3	71	12	.32	8.2	23	103	.34	8.6	0.085	2.2	4.00	SST	CG	N
0.850	21.59	72137	.88	22.4	.750	19.1	11	1.9	.69	17	7.5	33	.18	4.6	0.050	1.3	3.63	MW	CG	N
0.850	21.59	72137S	.88	22.4	.750	19.1	9.2	1.6	.55	14	5.1	23	.18	4.6	0.050	1.3	3.63	SST	CG	N
0.850	21.59	72147	.88	22.4	.740	18.8	15	2.6	.66	17	9.9	44	.21	5.2	0.055	1.4	3.75	MW	CG	N
0.850	21.59	72147S	.88	22.4	.740	18.8	13	2.2	.52	13	6.7	30	.21	5.2	0.055	1.4	3.75	SST	CG	N
0.850	21.59	72163	.88	22.4	.716	18.2	28	5.0	.60	15	17	76	.28	7.0	0.067	1.7	4.13	MW	CG	N
0.850	21.59	72163S	.88	22.4	.716	18.2	24	4.2	.50	13	12	54	.28	7.0	0.067	1.7	4.13	SST	CG	N
0.850	21.59	72173	.88	22.4	.714	18.1	30	5.2	.60	15	18	79	.28	7.1	0.068	1.7	4.13	MW	CG	N
0.850	21.59	72173S	.88	22.4	.714	18.1	25	4.4	.50	13	13	56	.28	7.1	0.068	1.7	4.13	SST	CG	N
0.850	21.59	72186	.88	22.4	.706	17.9	41	7.1	.52	13	21	94	.29	7.3	0.072	1.8	4.00	MW	CG	N
0.850	21.59	72186S	.88	22.4	.706	17.9	35	6.0	.41	10	14	63	.29	7.3	0.072	1.8	4.00	SST	CG	N
0.850	21.59	72195	.88	22.4	.702	17.8	40	7.0	.57	14	23	101	.31	8.0	0.074	1.9	4.25	MW	CG	N
0.850	21.59	72195S	.88	22.4	.702	17.8	34	6.0	.45	11	15	68	.31	8.0	0.074	1.9	4.25	SST	CG	N
0.850	21.59	72212	.88	22.4	.690	17.5	55	9.6	.52	13	29	128	.35	8.9	0.080	2.0	4.38	MW	CG	N
0.850	21.59	72212S	.88	22.4	.690	17.5	47	8.2	.41	10	19	86	.35	8.9	0.080	2.0	4.38	SST	CG	N
0.850	21.59	72234	.88	22.4	.688	17.5	57	9.9	.53	13	30	132	.35	9.0	0.081	2.1	4.38	MW	CG	N
0.850	21.59	72234S	.88	22.4	.688	17.5	48	8.4	.42	11	20	89	.35	9.0	0.081	2.1	4.38	SST	CG	N
0.850	21.59	72247	.88	22.4	.680	17.3	67	12	.50	13	33	148	.38	9.7	0.085	2.2	4.50	MW	CG	N
0.850	21.59	72247S	.88	22.4	.680	17.3	57	10	.41	10	23	103	.38	9.7	0.085	2.2	4.50	SST	CG	N
0.850	21.59	72262	.88	22.4	.668	17.0	90	16	.45	11	40	180	.41	10.4	0.091	2.3	4.50	MW	CG	N
0.850	21.59	72262S	.88	22.4	.668	17.0	76	13	.35	8.9	27	119	.41	10.4	0.091	2.3	4.50	SST	CG	N
0.850	21.59	72276	.88	22.4	.666	16.9	90	16	.45	12	41	182	.43	10.8	0.092	2.3	4.63	MW	CG	N
0.850	21.59	72276S	.88	22.4	.666	16.9	77	13	.36	9.2	28	123	.43	10.8	0.092	2.3	4.63	SST	CG	N
0.850	21.59	72138	1.00	25.4	.750	19.1	9.4	1.6	.80	20	7.5	33	.19	4.9	0.050	1.3	3.88	MW	CG	N
0.850	21.59	72138S	1.00	25.4	.750	19.1	8.0	1.4	.64	16	5.1	23	.19	4.9	0.050	1.3	3.88	SST	CG	N
0.850	21.59	72148	1.00	25.4	.740	18.8	13	2.3	.77	19	9.9	44	.22	5.6	0.055	1.4	4.00	MW	CG	N
0.850	21.59	72148S	1.00	25.4	.740	18.8	11	1.9	.61	15	6.7	30	.22	5.6	0.055	1.4	4.00	SST	CG	N
0.850	21.59	72164	1.00	25.4	.716	18.2	24	4.3	.70	18	17	76	.30	7.7	0.067	1.7	4.50	MW	CG	N
0.850	21.59	72164S	1.00	25.4	.716	18.2	21	3.6	.58	15	12	54	.30	7.7	0.067	1.7	4.50	SST	CG	N
0.850	21.59	72174	1.00	25.4	.714	18.1	26	4.5	.69	18	18	79	.31	7.8	0.068	1.7	4.50	MW	CG	N
0.850	21.59	72174S	1.00	25.4	.714	18.1	22	3.8	.58	15	13	56	.31	7.8	0.068	1.7	4.50	SST	CG	N
0.850	21.59	72187	1.00	25.4	.706	17.9	35	6.1	.60	15	21	94	.32	8.0	0.072	1.8	4.38	MW	CG	N
0.850	21.59	72187S	1.00	25.4	.706	17.9	30	5.2	.48	12	14	63	.32	8.0	0.072	1.8	4.38	SST	CG	N
0.850	21.59	72196	1.00	25.4	.702	17.8	34	6.0	.65	16	22	99	.35	8.9	0.074	1.9	4.75	MW	CG	N
0.850	21.59	72196S	1.00	25.4	.702	17.8	29	5.1	.53	13	15	68	.35	8.9	0.074	1.9	4.75	SST	CG	N
0.850	21.59	72214	1.00	25.4	.690	17.5	47	8.2	.62	16	29	128	.38	9.7	0.080	2.0	4.75	MW	CG	N
0.850	21.59	72214S	1.00	25.4	.690	17.5	40	7.0	.49	12	19	86	.38	9.7	0.080	2.0	4.75	SST	CG	N
0.850	21.59	72235	1.00	25.4	.688	17.5	48	8.4	.61	15	29	129	.39	10.0	0.081	2.1	4.88	MW	CG	N
0.850	21.59	72235S	1.00	25.4	.688	17.5	41	7.1	.49	12	20	89	.39	10.0	0.081	2.1	4.88	SST	CG	N
0.850	21.59	72248	1.00	25.4	.680	17.3	59	10	.58	15	34	153	.41	10.5	0.085	2.2	4.88	MW	CG	N
0.850	21.59	72248S	1.00	25.4	.680	17.3	50	8.8	.46	12	23	103	.41	10.5	0.085	2.2	4.88	SST	CG	N
0.850	21.59	72264	1.00	25.4	.668	17.0	76	13	.53	14	40	180	.46	11.6	0.091	2.3	5.00	MW	CG	N
0.850	21.59	72264S	1.00	25.4	.668	17.0	65	11	.41	11	27	119	.46	11.6	0.091	2.3	5.00	SST	CG	N
0.850	21.59	72277	1.00	25.4	.666	16.9	77	13	.53	13	41	181	.47	12.0	0.092	2.3	5.13	MW	CG	N
0.850	21.59	72277S	1.00	25.4	.666	16.9	65	11	.42	11	28	123	.47	12.0	0.092	2.3	5.13	SST	CG	N
0.850	21.59	72287	1.00	25.4	.654	16.6	100	18	.50	13	50	222	.50	12.8	0.098	2.5	5.13	MW	CG	N
0.850	21.59	72287S	1.00	25.4	.654	16.6	85	15	.39	9.9	33	148	.50	12.8	0.098	2.5	5.13	SST	CG	N
0.850	21.59	72297	1.00	25.4	.650	16.5	125	22	.43	11	53	237	.48	12.1	0.100	2.5	4.75	MW	CG	N
0.850	21.59	72297S	1.00	25.4	.650	16.5	106	19	.33	8.5	35	157	.48	12.1	0.100	2.5	4.75	SST	CG	N
0.850	21.59	72308	1.00	25.4	.640	16.														



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.850	21.59	72278S	1.25	31.8	.666	16.9	50	8.8	.55	14	28	123	.55	14.0	0.092	2.3	6.00	SST	CG	N
0.850	21.59	72288	1.25	31.8	.654	16.6	77	13	.65	17	50	222	.60	15.2	0.098	2.5	6.13	MW	CG	N
0.850	21.59	72288S	1.25	31.8	.654	16.6	65	11	.51	13	33	148	.60	15.2	0.098	2.5	6.13	SST	CG	N
0.850	21.59	72298	1.25	31.8	.650	16.5	95	17	.56	14	53	237	.56	14.3	0.100	2.5	5.63	MW	CG	N
0.850	21.59	72298S	1.25	31.8	.650	16.5	81	14	.44	11	35	157	.56	14.3	0.100	2.5	5.63	SST	CG	N
0.850	21.59	72310	1.25	31.8	.640	16.3	103	18	.60	15	62	274	.64	16.3	0.105	2.7	6.13	MW	CG	N
0.850	21.59	72310S	1.25	31.8	.640	16.3	87	15	.47	12	41	181	.64	16.3	0.105	2.7	6.13	SST	CG	N
0.850	21.59	72237	1.38	35.1	.688	17.5	34	6.0	.88	22	30	133	.49	12.3	0.081	2.1	6.00	MW	CG	N
0.850	21.59	72237S	1.38	35.1	.688	17.5	29	5.1	.69	18	20	89	.49	12.3	0.081	2.1	6.00	SST	CG	N
0.850	21.59	72250	1.38	35.1	.680	17.3	42	7.4	.82	21	34	153	.51	13.0	0.085	2.2	6.00	MW	CG	N
0.850	21.59	72250S	1.38	35.1	.680	17.3	36	6.3	.65	16	23	103	.51	13.0	0.085	2.2	6.00	SST	CG	N
0.850	21.59	72140	1.50	38.1	.750	19.1	6.0	1.1	1.2	32	7.5	33	.24	6.2	0.050	1.3	4.88	MW	CG	N
0.850	21.59	72140S	1.50	38.1	.750	19.1	5.1	.90	.99	25	5.1	23	.24	6.2	0.050	1.3	4.88	SST	CG	N
0.850	21.59	72150	1.50	38.1	.740	18.8	8.3	1.5	1.2	30	9.9	44	.28	7.2	0.055	1.4	5.13	MW	CG	N
0.850	21.59	72150S	1.50	38.1	.740	18.8	7.1	1.2	.95	24	6.7	30	.28	7.2	0.055	1.4	5.13	SST	CG	N
0.850	21.59	72166	1.50	38.1	.716	18.2	15	2.7	1.1	28	17	76	.39	10.0	0.067	1.7	5.88	MW	CG	N
0.850	21.59	72166S	1.50	38.1	.716	18.2	13	2.3	.92	23	12	54	.39	10.0	0.067	1.7	5.88	SST	CG	N
0.850	21.59	72176	1.50	38.1	.714	18.1	16	2.8	1.1	28	18	78	.41	10.4	0.068	1.7	6.00	MW	CG	N
0.850	21.59	72176S	1.50	38.1	.714	18.1	14	2.4	.92	23	13	56	.41	10.4	0.068	1.7	6.00	SST	CG	N
0.850	21.59	72189	1.50	38.1	.706	17.9	22	3.8	.97	25	21	94	.41	10.5	0.072	1.8	5.75	MW	CG	N
0.850	21.59	72189S	1.50	38.1	.706	17.9	19	3.2	.76	19	14	63	.41	10.5	0.072	1.8	5.75	SST	CG	N
0.850	21.59	72198	1.50	38.1	.702	17.8	22	3.8	1.0	26	22	100	.46	11.7	0.074	1.9	6.25	MW	CG	N
0.850	21.59	72198S	1.50	38.1	.702	17.8	18	3.2	.83	21	15	68	.46	11.7	0.074	1.9	6.25	SST	CG	N
0.850	21.59	72218	1.50	38.1	.690	17.5	29	5.1	.98	25	29	128	.51	13.0	0.080	2.0	6.38	MW	CG	N
0.850	21.59	72218S	1.50	38.1	.690	17.5	25	4.4	.77	20	19	86	.51	13.0	0.080	2.0	6.38	SST	CG	N
0.850	21.59	72238	1.50	38.1	.688	17.5	30	5.3	.97	25	30	131	.53	13.4	0.081	2.1	6.50	MW	CG	N
0.850	21.59	72238S	1.50	38.1	.688	17.5	26	4.5	.78	20	20	89	.53	13.4	0.081	2.1	6.50	SST	CG	N
0.850	21.59	72251	1.50	38.1	.680	17.3	37	6.4	.94	24	34	153	.56	14.3	0.085	2.2	6.63	MW	CG	N
0.850	21.59	72251S	1.50	38.1	.680	17.3	31	5.5	.74	19	23	103	.56	14.3	0.085	2.2	6.63	SST	CG	N
0.850	21.59	72267	1.50	38.1	.668	17.0	49	8.6	.83	21	40	180	.60	15.3	0.091	2.3	6.63	MW	CG	N
0.850	21.59	72267S	1.50	38.1	.668	17.0	42	7.3	.64	16	27	119	.60	15.3	0.091	2.3	6.63	SST	CG	N
0.850	21.59	72279	1.50	38.1	.666	16.9	48	8.4	.86	22	41	182	.64	16.4	0.092	2.3	7.00	MW	CG	N
0.850	21.59	72279S	1.50	38.1	.666	16.9	41	7.1	.68	17	28	123	.64	16.4	0.092	2.3	7.00	SST	CG	N
0.850	21.59	72289	1.50	38.1	.654	16.6	63	11	.80	20	50	224	.69	17.4	0.098	2.5	7.00	MW	CG	N
0.850	21.59	72289S	1.50	38.1	.654	16.6	53	9.4	.62	16	33	148	.69	17.4	0.098	2.5	7.00	SST	CG	N
0.850	21.59	72299	1.50	38.1	.650	16.5	77	13	.69	18	53	237	.65	16.5	0.100	2.5	6.50	MW	CG	N
0.850	21.59	72299S	1.50	38.1	.650	16.5	65	11	.54	14	35	157	.65	16.5	0.100	2.5	6.50	SST	CG	N
0.850	21.59	72312	1.50	38.1	.640	16.3	83	14	.74	19	62	274	.75	19.0	0.105	2.7	7.13	MW	CG	N
0.850	21.59	72312S	1.50	38.1	.640	16.3	70	12	.58	15	41	181	.75	19.0	0.105	2.7	7.13	SST	CG	N
0.850	21.59	72152	1.75	44.5	.740	18.8	7.1	1.2	1.4	36	9.9	44	.32	8.0	0.055	1.4	5.75	MW	CG	N
0.850	21.59	72152S	1.75	44.5	.740	18.8	6.0	1.1	1.1	28	6.7	30	.32	8.0	0.055	1.4	5.75	SST	CG	N
0.850	21.59	72177	1.75	44.5	.714	18.1	14	2.4	1.3	33	18	78	.46	11.7	0.068	1.7	6.75	MW	CG	N
0.850	21.59	72177S	1.75	44.5	.714	18.1	12	2.0	1.1	28	13	56	.46	11.7	0.068	1.7	6.75	SST	CG	N
0.850	21.59	72190	1.75	44.5	.706	17.9	18	3.2	1.1	29	21	94	.47	11.9	0.072	1.8	6.50	MW	CG	N
0.850	21.59	72190S	1.75	44.5	.706	17.9	16	2.7	.91	23	14	63	.47	11.9	0.072	1.8	6.50	SST	CG	N
0.850	21.59	72200	1.75	44.5	.702	17.8	19	3.3	1.2	31	23	102	.51	12.9	0.074	1.9	6.88	MW	CG	N
0.850	21.59	72200S	1.75	44.5	.702	17.8	16	2.8	.95	24	15	68	.51	12.9	0.074	1.9	6.88	SST	CG	N
0.850	21.59	72220	1.75	44.5	.690	17.5	25	4.3	1.2	30	29	128	.58	14.7	0.080	2.0	7.25	MW	CG	N
0.850	21.59	72220S	1.75	44.5	.690	17.5	21	3.7	.92	23	19	86	.58	14.7	0.080	2.0	7.25	SST	CG	N
0.850	21.59	72239	1.75	44.5	.688	17.5	26	4.5	1.2	29	29	131	.60	15.2	0.081	2.1	7.38	MW	CG	N
0.850	21.59	72239S	1.75	44.5	.688	17.5	22	3.8	.92	23	20	89	.60	15.2	0.081	2.1	7.38	SST	CG	N
0.850	21.59	72252	1.75	44.5	.680	17.3	31	5.4	1.1	28	34	153	.63	15.9	0.085	2.2	7.38	MW	CG	N
0.850	21.59	72252S	1.75	44.5	.680	17.3	26	4.6	.88	22	23	103	.63	15.9	0.085	2.2	7.38	SST	CG	N
0.850	21.59	72268	1.75	44.5	.668	17.0	41	7.2	.99	25	40	180	.68	17.3	0.091	2.3	7.50	MW	CG	N
0.850	21.59	72268S	1.75	44.5	.668	17.0	35	6.1	.77	20	27	119	.68	17.3	0.091	2.3	7.50	SST	CG	N
0.850	21.59	72280	1.75	44.5	.666	16.9	40	7.0	1.0	26	41	182	.72	18.4	0.092	2.3	7.88	MW	CG	N
0.850	21.59	72280S	1.75	44.5	.666	16.9	34	6.0	.81	21	28	123	.72	18.4	0.092	2.3	7.88	SST	CG	N
0.850	21.59	72290	1.75	44.5	.654	16.6	53	9.2	.96	24										




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.850	21.59	72253S	2.00	50.8	.680	17.3	22	3.9	1.0	26	23	103	.71	18.1	0.085	2.2	8.38	SST	CG	N
0.850	21.59	72269	2.00	50.8	.668	17.0	35	6.1	1.2	29	40	180	.77	19.6	0.091	2.3	8.50	MW	CG	N
0.850	21.59	72269S	2.00	50.8	.668	17.0	30	5.2	.90	23	27	119	.77	19.6	0.091	2.3	8.50	SST	CG	N
0.850	21.59	72281	2.00	50.8	.666	16.9	35	6.0	1.2	30	41	182	.82	20.7	0.092	2.3	8.88	MW	CG	N
0.850	21.59	72281S	2.00	50.8	.666	16.9	29	5.1	.94	24	28	123	.82	20.7	0.092	2.3	8.88	SST	CG	N
0.850	21.59	72291	2.00	50.8	.654	16.6	45	7.9	1.1	28	50	224	.87	22.1	0.098	2.5	8.88	MW	CG	N
0.850	21.59	72291S	2.00	50.8	.654	16.6	38	6.7	.87	22	33	148	.87	22.1	0.098	2.5	8.88	SST	CG	N
0.850	21.59	72301	2.00	50.8	.650	16.5	55	9.7	.96	24	53	237	.81	20.6	0.100	2.5	8.13	MW	CG	N
0.850	21.59	72301S	2.00	50.8	.650	16.5	47	8.2	.75	19	35	157	.81	20.6	0.100	2.5	8.13	SST	CG	N
0.850	21.59	72316	2.00	50.8	.640	16.3	60	10	1.0	26	62	274	.96	24.3	0.105	2.7	9.13	MW	CG	N
0.850	21.59	72316S	2.00	50.8	.640	16.3	51	8.9	.80	20	41	181	.96	24.3	0.105	2.7	9.13	SST	CG	N
0.850	21.59	72155	2.25	57.2	.740	18.8	5.4	.95	1.8	47	9.9	44	.38	9.6	0.055	1.4	6.88	MW	CG	N
0.850	21.59	72155S	2.25	57.2	.740	18.8	4.6	.80	1.5	37	6.7	30	.38	9.6	0.055	1.4	6.88	SST	CG	N
0.850	21.59	72179	2.25	57.2	.714	18.1	10	1.8	1.7	43	18	79	.55	14.0	0.068	1.7	8.13	MW	CG	N
0.850	21.59	72179S	2.25	57.2	.714	18.1	8.8	1.5	1.4	36	13	56	.55	14.0	0.068	1.7	8.13	SST	CG	N
0.850	21.59	72203	2.25	57.2	.702	17.8	14	2.5	1.6	40	23	102	.62	15.7	0.074	1.9	8.38	MW	CG	N
0.850	21.59	72203S	2.25	57.2	.702	17.8	12	2.1	1.3	32	15	68	.62	15.7	0.074	1.9	8.38	SST	CG	N
0.850	21.59	72224	2.25	57.2	.690	17.5	19	3.3	1.5	39	29	128	.71	18.0	0.080	2.0	8.88	MW	CG	N
0.850	21.59	72224S	2.25	57.2	.690	17.5	16	2.8	1.2	31	19	86	.71	18.0	0.080	2.0	8.88	SST	CG	N
0.850	21.59	72241	2.25	57.2	.688	17.5	19	3.4	1.5	39	29	131	.73	18.5	0.081	2.1	9.00	MW	CG	N
0.850	21.59	72241S	2.25	57.2	.688	17.5	16	2.9	1.2	31	20	89	.73	18.5	0.081	2.1	9.00	SST	CG	N
0.850	21.59	72254	2.25	57.2	.680	17.3	23	4.1	1.5	37	34	153	.78	19.7	0.085	2.2	9.13	MW	CG	N
0.850	21.59	72254S	2.25	57.2	.680	17.3	20	3.5	1.2	30	23	103	.78	19.7	0.085	2.2	9.13	SST	CG	N
0.850	21.59	72270	2.25	57.2	.668	17.0	31	5.4	1.3	33	40	180	.84	21.4	0.091	2.3	9.25	MW	CG	N
0.850	21.59	72270S	2.25	57.2	.668	17.0	26	4.6	1.0	26	27	119	.84	21.4	0.091	2.3	9.25	SST	CG	N
0.850	21.59	72282	2.25	57.2	.666	16.9	30	5.3	1.4	34	41	183	.90	22.8	0.092	2.3	9.75	MW	CG	N
0.850	21.59	72282S	2.25	57.2	.666	16.9	26	4.5	1.1	27	28	123	.90	22.8	0.092	2.3	9.75	SST	CG	N
0.850	21.59	72292	2.25	57.2	.654	16.6	39	6.9	1.3	32	50	224	.97	24.6	0.098	2.5	9.88	MW	CG	N
0.850	21.59	72292S	2.25	57.2	.654	16.6	33	5.8	1.0	25	33	148	.97	24.6	0.098	2.5	9.88	SST	CG	N
0.850	21.59	72302	2.25	57.2	.650	16.5	49	8.5	1.1	28	53	237	.90	22.9	0.100	2.5	9.00	MW	CG	N
0.850	21.59	72302S	2.25	57.2	.650	16.5	41	7.2	.85	22	35	157	.90	22.9	0.100	2.5	9.00	SST	CG	N
0.850	21.59	72318	2.25	57.2	.640	16.3	52	9.2	1.2	30	62	274	1.06	27.0	0.105	2.7	10.1	MW	CG	N
0.850	21.59	72318S	2.25	57.2	.640	16.3	44	7.8	.92	23	41	181	1.06	27.0	0.105	2.7	10.1	SST	CG	N
0.850	21.59	72142	2.50	63.5	.750	19.1	3.5	.61	2.1	54	7.5	33	.35	8.9	0.050	1.3	7.00	MW	CG	N
0.850	21.59	72142S	2.50	63.5	.750	19.1	3.0	.52	1.7	43	5.1	23	.35	8.9	0.050	1.3	7.00	SST	CG	N
0.850	21.59	72156	2.50	63.5	.740	18.8	4.8	.85	2.1	52	9.9	44	.41	10.3	0.055	1.4	7.38	MW	CG	N
0.850	21.59	72156S	2.50	63.5	.740	18.8	4.1	.72	1.6	42	6.7	30	.41	10.3	0.055	1.4	7.38	SST	CG	N
0.850	21.59	72168	2.50	63.5	.716	18.2	8.9	1.6	1.9	49	17	76	.59	14.9	0.067	1.7	8.75	MW	CG	N
0.850	21.59	72168S	2.50	63.5	.716	18.2	7.6	1.3	1.6	41	12	54	.59	14.9	0.067	1.7	8.75	SST	CG	N
0.850	21.59	72180	2.50	63.5	.714	18.1	9.3	1.6	1.9	48	18	78	.60	15.3	0.068	1.7	8.88	MW	CG	N
0.850	21.59	72180S	2.50	63.5	.714	18.1	7.9	1.4	1.6	41	13	56	.60	15.3	0.068	1.7	8.88	SST	CG	N
0.850	21.59	72192	2.50	63.5	.706	17.9	12	2.2	1.7	43	21	94	.62	15.8	0.072	1.8	8.63	MW	CG	N
0.850	21.59	72192S	2.50	63.5	.706	17.9	11	1.9	1.3	34	14	63	.62	15.8	0.072	1.8	8.63	SST	CG	N
0.850	21.59	72204	2.50	63.5	.702	17.8	12	2.2	1.8	46	22	99	.70	17.9	0.074	1.9	9.50	MW	CG	N
0.850	21.59	72204S	2.50	63.5	.702	17.8	11	1.8	1.5	37	15	68	.70	17.9	0.074	1.9	9.50	SST	CG	N
0.850	21.59	72226	2.50	63.5	.690	17.5	17	2.9	1.7	44	29	128	.77	19.6	0.080	2.0	9.63	MW	CG	N
0.850	21.59	72226S	2.50	63.5	.690	17.5	14	2.5	1.4	34	19	86	.77	19.6	0.080	2.0	9.63	SST	CG	N
0.850	21.59	72242	2.50	63.5	.688	17.5	17	3.0	1.7	43	29	130	.80	20.3	0.081	2.1	9.88	MW	CG	N
0.850	21.59	72242S	2.50	63.5	.688	17.5	15	2.6	1.4	35	20	89	.80	20.3	0.081	2.1	9.88	SST	CG	N
0.850	21.59	72255	2.50	63.5	.680	17.3	21	3.7	1.7	42	34	153	.85	21.6	0.085	2.2	10.0	MW	CG	N
0.850	21.59	72255S	2.50	63.5	.680	17.3	18	3.1	1.3	33	23	103	.85	21.6	0.085	2.2	10.0	SST	CG	N
0.850	21.59	72271	2.50	63.5	.668	17.0	28	4.9	1.4	37	40	180	.91	23.1	0.091	2.3	10.0	MW	CG	N
0.850	21.59	72271S	2.50	63.5	.668	17.0	24	4.2	1.1	29	27	119	.91	23.1	0.091	2.3	10.0	SST	CG	N
0.850	21.59	72283	2.50	63.5	.666	16.9	27	4.7	1.5	38	41	182	.99	25.1	0.092	2.3	10.8	MW	CG	N
0.850	21.59	72283S	2.50	63.5	.666	16.9	23	4.0	1.2	31	28	123	.99	25.1	0.092	2.3	10.8	SST	CG	N
0.850	21.59	72293	2.50	63.5	.654	16.6	35	6.2	1.4	36	50	224	1.07	27.1	0.098	2.5	10.9	MW	CG	N
0.850	21.59	72293S	2.50	63.5	.654	16.6	30													



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.850	21.59	72304S	2.75	69.9	.650	16.5	33	5.8	1.1	27	35	157	1.08	27.3	0.100	2.5	10.8	SST	CG	N
0.850	21.59	72322	2.75	69.9	.640	16.3	42	7.4	1.5	37	62	274	1.26	32.0	0.105	2.7	12.0	MW	CG	N
0.850	21.59	72322S	2.75	69.9	.640	16.3	36	6.3	1.1	29	41	181	1.26	32.0	0.105	2.7	12.0	SST	CG	N
0.850	21.59	72143	3.00	76.2	.750	19.1	2.9	.51	2.6	65	7.5	33	.40	10.2	0.050	1.3	8.00	MW	CG	N
0.850	21.59	72143S	3.00	76.2	.750	19.1	2.5	.43	2.0	52	5.1	23	.40	10.2	0.050	1.3	8.00	SST	CG	N
0.850	21.59	72159	3.00	76.2	.740	18.8	4.0	.70	2.5	63	9.9	44	.47	11.9	0.055	1.4	8.50	MW	CG	N
0.850	21.59	72159S	3.00	76.2	.740	18.8	3.4	.60	2.0	50	6.7	30	.47	11.9	0.055	1.4	8.50	SST	CG	N
0.850	21.59	72169	3.00	76.2	.716	18.2	7.3	1.3	2.3	59	17	76	.69	17.4	0.067	1.7	10.3	MW	CG	N
0.850	21.59	72169S	3.00	76.2	.716	18.2	6.2	1.1	1.9	49	12	54	.69	17.4	0.067	1.7	10.3	SST	CG	N
0.850	21.59	72183	3.00	76.2	.714	18.1	7.7	1.3	2.3	58	18	79	.71	17.9	0.068	1.7	10.4	MW	CG	N
0.850	21.59	72183S	3.00	76.2	.714	18.1	6.5	1.1	1.9	49	13	56	.71	17.9	0.068	1.7	10.4	SST	CG	N
0.850	21.59	72193	3.00	76.2	.706	17.9	10	1.8	2.0	52	21	94	.71	18.1	0.072	1.8	9.88	MW	CG	N
0.850	21.59	72193S	3.00	76.2	.706	17.9	8.8	1.5	1.6	41	14	63	.71	18.1	0.072	1.8	9.88	SST	CG	N
0.850	21.59	72207	3.00	76.2	.702	17.8	10	1.8	2.2	56	22	99	.81	20.7	0.074	1.9	11.0	MW	CG	N
0.850	21.59	72207S	3.00	76.2	.702	17.8	8.7	1.5	1.8	45	15	68	.81	20.7	0.074	1.9	11.0	SST	CG	N
0.850	21.59	72230	3.00	76.2	.690	17.5	14	2.4	2.1	53	29	128	.90	22.9	0.080	2.0	11.3	MW	CG	N
0.850	21.59	72230S	3.00	76.2	.690	17.5	12	2.1	1.6	41	19	86	.90	22.9	0.080	2.0	11.3	SST	CG	N
0.850	21.59	72244	3.00	76.2	.688	17.5	14	2.5	2.1	53	29	131	.93	23.7	0.081	2.1	11.5	MW	CG	N
0.850	21.59	72244S	3.00	76.2	.688	17.5	12	2.1	1.7	42	20	89	.93	23.7	0.081	2.1	11.5	SST	CG	N
0.850	21.59	72257	3.00	76.2	.680	17.3	17	3.0	2.0	50	34	153	.99	25.1	0.085	2.2	11.6	MW	CG	N
0.850	21.59	72257S	3.00	76.2	.680	17.3	15	2.6	1.6	40	23	103	.99	25.1	0.085	2.2	11.6	SST	CG	N
0.850	21.59	72273	3.00	76.2	.668	17.0	23	4.0	1.8	45	40	180	1.07	27.2	0.091	2.3	11.8	MW	CG	N
0.850	21.59	72273S	3.00	76.2	.668	17.0	20	3.4	1.4	35	27	119	1.07	27.2	0.091	2.3	11.8	SST	CG	N
0.850	21.59	72285	3.00	76.2	.666	16.9	22	3.9	1.8	47	41	182	1.16	29.5	0.092	2.3	12.6	MW	CG	N
0.850	21.59	72285S	3.00	76.2	.666	16.9	19	3.3	1.5	37	28	123	1.16	29.5	0.092	2.3	12.6	SST	CG	N
0.850	21.59	72295	3.00	76.2	.654	16.6	29	5.1	1.7	44	50	224	1.25	31.7	0.098	2.5	12.8	MW	CG	N
0.850	21.59	72295S	3.00	76.2	.654	16.6	25	4.3	1.4	34	33	148	1.25	31.7	0.098	2.5	12.8	SST	CG	N
0.850	21.59	72305	3.00	76.2	.650	16.5	36	6.2	1.5	38	53	237	1.16	29.5	0.100	2.5	11.6	MW	CG	N
0.850	21.59	72305S	3.00	76.2	.650	16.5	30	5.3	1.2	30	35	157	1.16	29.5	0.100	2.5	11.6	SST	CG	N
0.850	21.59	72324	3.00	76.2	.640	16.3	38	6.7	1.6	41	62	274	1.38	35.0	0.105	2.7	13.1	MW	CG	N
0.850	21.59	72324S	3.00	76.2	.640	16.3	32	5.7	1.3	32	41	181	1.38	35.0	0.105	2.7	13.1	SST	CG	N
0.850	21.59	72258	3.25	82.6	.680	17.3	15	2.7	2.1	54	33	146	1.11	28.1	0.085	2.2	13.0	MW	CG	N
0.850	21.59	72258S	3.25	82.6	.680	17.3	13	2.3	1.8	45	23	103	1.11	28.1	0.085	2.2	13.0	SST	CG	N
0.850	21.59	72144	3.50	88.9	.750	19.1	2.5	.43	3.0	77	7.5	33	.46	11.6	0.050	1.3	9.13	MW	CG	N
0.850	21.59	72144S	3.50	88.9	.750	19.1	2.1	.37	2.4	61	5.1	23	.46	11.6	0.050	1.3	9.13	SST	CG	N
0.850	21.59	72160	3.50	88.9	.740	18.8	3.4	.60	2.9	74	9.9	44	.53	13.4	0.055	1.4	9.63	MW	CG	N
0.850	21.59	72160S	3.50	88.9	.740	18.8	2.9	.51	2.3	59	6.7	30	.53	13.4	0.055	1.4	9.63	SST	CG	N
0.850	21.59	72170	3.50	88.9	.716	18.2	6.3	1.1	2.7	69	17	76	.78	19.8	0.067	1.7	11.6	MW	CG	N
0.850	21.59	72170S	3.50	88.9	.716	18.2	5.3	.93	2.3	58	12	54	.78	19.8	0.067	1.7	11.6	SST	CG	N
0.850	21.59	72184	3.50	88.9	.714	18.1	6.5	1.1	2.7	68	18	78	.81	20.5	0.068	1.7	11.9	MW	CG	N
0.850	21.59	72184S	3.50	88.9	.714	18.1	5.5	.97	2.3	58	13	56	.81	20.5	0.068	1.7	11.9	SST	CG	N
0.850	21.59	72194	3.50	88.9	.706	17.9	8.8	1.5	2.4	61	21	94	.81	20.6	0.072	1.8	11.3	MW	CG	N
0.850	21.59	72194S	3.50	88.9	.706	17.9	7.5	1.3	1.9	48	14	63	.81	20.6	0.072	1.8	11.3	SST	CG	N
0.850	21.59	72208	3.50	88.9	.702	17.8	8.7	1.5	2.6	65	22	99	.93	23.7	0.074	1.9	12.6	MW	CG	N
0.850	21.59	72208S	3.50	88.9	.702	17.8	7.4	1.3	2.1	53	15	68	.93	23.7	0.074	1.9	12.6	SST	CG	N
0.850	21.59	72232	3.50	88.9	.690	17.5	12	2.1	2.4	62	29	128	1.03	26.2	0.080	2.0	12.9	MW	CG	N
0.850	21.59	72232S	3.50	88.9	.690	17.5	10	1.8	1.9	49	19	86	1.03	26.2	0.080	2.0	12.9	SST	CG	N
0.850	21.59	72245	3.50	88.9	.688	17.5	12	2.1	2.4	61	29	129	1.08	27.5	0.081	2.1	13.4	MW	CG	N
0.850	21.59	72245S	3.50	88.9	.688	17.5	10	1.8	2.0	50	20	89	1.08	27.5	0.081	2.1	13.4	SST	CG	N
0.850	21.59	72259	3.50	88.9	.680	17.3	15	2.6	2.4	60	34	153	1.15	29.1	0.085	2.2	13.5	MW	CG	N
0.850	21.59	72259S	3.50	88.9	.680	17.3	12	2.2	1.9	47	23	103	1.15	29.1	0.085	2.2	13.5	SST	CG	N
0.850	21.59	72275	3.50	88.9	.668	17.0	19	3.3	2.2	55	40	180	1.27	32.4	0.091	2.3	14.0	MW	CG	N
0.850	21.59	72275S	3.50	88.9	.668	17.0	16	2.8	1.7	43	27	119	1.27	32.4	0.091	2.3	14.0	SST	CG	N
0.850	21.59	72286	3.50	88.9	.666	16.9	19	3.3	2.2	55	41	182	1.33	33.9	0.092	2.3	14.5	MW	CG	N
0.850	21.59	72286S	3.50	88.9	.666	16.9	16	2.8	1.7	44	28	123	1.33	33.9	0.092	2.3	14.5	SST	CG	N
0.850	21.59	72296	3.50	88.9	.654	16.6	25	4.3	2.0	52	50	224	1.43	36.4	0.098	2.5	14.6	MW	CG	N
0.850	21.59	72296S	3.50	88.9	.654	16.6	21	3.7	1.6	40	33	148	1.43	36.4	0.098	2.5	14.6			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.859	21.82	11710	.66	16.7	.743	18.9	21	3.7	.39	10	8.3	37	.20	5.2	0.058	1.5	3.50	SPR	CG	Z
0.859	21.82	11678	.72	18.2	.677	17.2	174	30	.16	4.2	29	127	.30	7.5	0.091	2.3	3.25	SPR	CG	Z
0.859	21.82	A13-35	.75	19.1	.793	20.1	1.3	.23	.59	15	.78	3.5	.17	4.2	0.033	0.8	4.00	SST	C	N
0.859	21.82	S-345	.75	19.1	.699	17.8	28	4.8	.27	6.9	7.5	33	.48	12.2	0.080	2.0	6.00	SST	CG	N
0.859	21.82	10793	.81	20.6	.639	16.2	162	28	.27	6.9	44	196	.52	13.3	0.110	2.8	4.75	SST	CG	N
0.859	21.82	S-3091	.88	22.2	.757	19.2	5.3	.94	.57	14	3.0	14	.31	7.8	0.051	1.3	5.00	SST	C	N
0.859	21.82	12284	.88	22.2	.695	17.7	69	12	.32	8.0	22	98	.33	8.3	0.082	2.1	4.00	SPR	CG	Z
0.859	21.82	KK-85	.88	22.2	.639	16.2	250	44	.19	4.9	48	215	.44	11.2	0.110	2.8	4.00	SPR	CG	N
0.859	21.82	12486	.91	23.0	.699	17.8	62	11	.33	8.3	20	91	.40	10.2	0.080	2.0	4.00	SPR	C	N
0.859	21.82	2951	.91	23.0	.669	17.0	131	23	.25	6.3	32	144	.38	9.7	0.095	2.4	4.00	SPR	CG	Z
0.859	21.82	B12-46	1.00	25.4	.765	19.4	4.0	.71	.71	18	2.8	13	.29	7.5	0.047	1.2	5.25	SPR	C	N
0.859	21.82	PP-92	1.00	25.4	.725	18.4	25	4.4	.47	12	12	53	.27	6.8	0.067	1.7	4.00	SST	CG	N
0.859	21.82	N-55	1.03	26.2	.739	18.8	9.1	1.6	.67	17	6.1	27	.36	9.1	0.060	1.5	6.00	SPR	CG	Z
0.859	21.82	K-50	1.13	28.6	.735	18.7	21	3.7	.48	12	10	45	.25	6.3	0.062	1.6	4.00	SPR	CG	N
0.859	21.82	S-185	1.25	31.8	.769	19.5	1.2	.21	.76	19	.90	4.0	.50	12.6	0.045	1.1	10.0	SST	C	N
0.859	21.82	B11-69	1.25	31.8	.753	19.1	8.7	1.5	.73	19	6.3	28	.24	6.1	0.053	1.3	4.50	SPR	CG	Z
0.859	21.82	A15-52	1.25	31.8	.737	18.7	14	2.5	.63	16	9.1	40	.30	7.6	0.061	1.5	4.75	SST	CG	N
0.859	21.82	11512	1.25	31.8	.731	18.6	19	3.4	.58	15	11	49	.35	8.9	0.064	1.6	4.50	SPR	CG	Z
0.859	21.82	10148	1.25	31.8	.723	18.4	23	4.0	.59	15	13	59	.32	8.2	0.068	1.7	4.75	SPR	CG	Z
0.859	21.82	12138	1.25	31.8	.699	17.8	25	4.4	.69	18	17	76	.56	14.2	0.080	2.0	7.00	SPR	CG	Z
0.859	21.82	12225	1.28	32.5	.751	19.1	12	2.1	.57	15	6.7	30	.27	6.9	0.054	1.4	4.00	SPR	C	Z
0.859	21.82	12488	1.28	32.5	.699	17.8	42	7.3	.49	12	20	91	.48	12.2	0.080	2.0	5.00	SPR	C	N
0.859	21.82	2773	1.41	35.7	.645	16.4	111	19	.58	15	64	286	.64	16.3	0.107	2.7	6.00	MW	CG	Z
0.859	21.82	S-1307	1.44	36.5	.725	18.4	14	2.5	.83	21	12	53	.37	9.4	0.067	1.7	5.50	SST	CG	N
0.859	21.82	3864	1.44	36.5	.723	18.4	21	3.6	.64	16	13	59	.41	10.4	0.068	1.7	5.00	SPR	C	Z
0.859	21.82	B7-65	1.50	38.1	.735	18.7	14	2.4	.72	18	10	45	.31	7.9	0.062	1.6	5.00	SPR	CG	N
0.859	21.82	11776	1.50	38.1	.723	18.4	18	3.1	.75	19	13	59	.44	11.2	0.068	1.7	5.50	SPR	C	Z
0.859	21.82	10023	1.50	38.1	.719	18.3	22	3.8	.64	16	14	61	.37	9.3	0.070	1.8	5.25	SPR	CG	Z
0.859	21.82	00-53	1.50	38.1	.639	16.2	137	24	.32	8.2	44	196	.58	14.7	0.110	2.8	5.25	SST	CG	N
0.859	21.82	B15-1	1.53	38.9	.779	19.8	1.1	.19	1.2	30	1.3	5.7	.34	8.6	0.040	1.0	7.50	SST	C	N
0.859	21.82	MM-88	1.59	40.5	.519	13.2	667	117	.24	6.1	160	713	1.28	32.4	0.170	4.3	7.50	SPR	CG	Z
0.859	21.82	S-73	1.63	41.3	.751	19.1	3.3	.57	1.2	30	3.8	17	.45	11.3	0.054	1.4	8.25	SST	CG	N
0.859	21.82	TT-69	1.63	41.3	.649	16.5	79	14	.51	13	40	180	.68	17.3	0.105	2.7	6.50	SST	CG	N
0.859	21.82	11435	1.63	41.3	.609	15.5	127	22	.50	13	63	282	1.13	28.6	0.125	3.2	9.00	SPR	CG	Z
0.859	21.82	10646	1.63	41.3	.567	14.4	360	63	.30	7.5	107	474	1.02	26.0	0.146	3.7	7.00	SPR	CG	Z
0.859	21.82	S-1175	1.75	44.5	.505	12.8	774	135	.21	5.2	159	709	1.24	31.5	0.177	4.5	7.00	SST	CG	N
0.859	21.82	3321	1.88	47.6	.575	14.6	248	43	.40	10	98	438	1.12	28.4	0.142	3.6	8.00	SPR	CG	Z
0.859	21.82	B8-33	1.94	49.2	.651	16.5	78	14	.54	14	42	188	.73	18.5	0.104	2.6	7.00	SPR	CG	N
0.859	21.82	B17-195	1.97	50.0	.499	12.7	599	105	.26	6.6	155	689	1.62	41.1	0.180	4.6	9.00	SST	CG	N
0.859	21.82	2776	2.00	50.8	.673	17.1	55	9.6	.56	14	31	136	.69	17.4	0.093	2.4	6.33	SPR	C	Z
0.859	21.82	10502	2.00	50.8	.663	16.8	43	7.5	.83	21	36	158	.88	22.4	0.098	2.5	9.00	SPR	CG	Z
0.859	21.82	12465	2.00	50.8	.619	15.7	123	22	.51	13	62	277	.96	24.4	0.120	3.0	8.00	SPR	CG	Z
0.859	21.82	S-459	2.06	52.4	.675	17.1	25	4.3	1.1	28	27	122	.92	23.4	0.092	2.3	10.0	SST	CG	N
0.859	21.82	KK-81	2.25	57.2	.539	13.7	460	81	.29	7.5	135	601	1.28	32.5	0.160	4.1	8.00	SPR	CG	Z
0.859	21.82	A13-39	2.34	59.5	.697	17.7	15	2.6	1.4	35	20	88	.81	20.6	0.081	2.1	10.0	SST	CG	N
0.859	21.82	10370	2.38	60.3	.709	18.0	11	1.9	1.5	38	16	72	.88	22.4	0.075	1.9	10.8	SPR	C	Z
0.859	21.82	S-465	2.44	61.9	.649	16.5	48	8.5	.84	21	40	180	.98	24.9	0.105	2.7	9.33	SST	CG	N
0.859	21.82	10829	2.50	63.5	.699	17.8	17	3.0	1.2	31	20	91	.75	19.0	0.080	2.0	9.33	SPR	CG	Z
0.859	21.82	11430	2.50	63.5	.659	16.7	36	6.4	.96	24	35	156	1.00	25.4	0.100	2.5	10.0	SST	CG	N
0.859	21.82	11174	2.53	64.3	.641	16.3	53	9.3	.84	21	45	200	1.09	27.7	0.109	2.8	10.0	SST	CG	N
0.859	21.82	S-381	2.63	66.7	.765	19.4	1.8	.31	2.2	57	3.9	17	.40	10.1	0.047	1.2	8.50	SST	CG	N
0.859	21.82	11510	2.63	66.7	.563	14.3	202	35	.55	14	111	493	1.85	47.0	0.148	3.8	11.5	SPR	CG	Z
0.859	21.82	11953	2.69	68.2	.687	17.4	24	4.3	1.0	26	25	112	.77	19.7	0.086	2.2	9.00	SPR	CG	Z
0.859	21.82	2908	2.75	69.9	.669	17.0	26	4.6	1.2	31	32	144	1.14	29.0	0.095	2.4	12.0	SPR	CG	Z
0.859	21.82	4305	2.75	69.9	.609	15.5	83	14	.85	22	70	312	1.59	40.5	0.125	3.2	12.8	SPR	CG	Z
0.859	21.82	11591	2.78	70.6	.643	16.3	58	10	.82	21	47	210	1.19	30.2	0.108	2.7	10.0	SPR	CG	GI
0.859	21.82	10935	2.84	72.2	.777	19.7	.93	.16	2.4	61	2.2	9.9	.45	11.5	0.0					




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.875	22.23	10469	.66	16.7	.751	19.1	40	6.9	.25	6.4	9.9	44	.25	6.3	0.062	1.6	3.00	SPR	C	Z
0.875	22.23	3702	.66	16.7	.635	16.1	346	61	.18	4.5	61	271	.48	12.2	0.120	3.0	4.00	SPR	CG	Z
0.875	22.23	10942	.69	17.4	.605	15.4	1178	206	.07	1.8	84	372	.41	10.3	0.135	3.4	3.00	SPR	CG	Z
0.875	22.23	11386	.75	19.1	.785	19.9	4.6	.80	.57	14	2.6	12	.18	4.6	0.045	1.1	4.00	SST	CG	N
0.875	22.23	S-3177	.75	19.1	.767	19.5	15	2.7	.40	10	6.2	28	.18	4.5	0.054	1.4	3.25	SST	CG	N
0.875	22.23	1733	.75	19.1	.751	19.1	14	2.5	.39	10	5.6	25	.36	9.1	0.062	1.6	4.75	HD	C	Z
0.875	22.23	S-1438	.81	20.6	.825	21.0	.27	.05	.66	17	.18	.78	.15	3.8	0.025	0.6	5.00	SST	C	N
0.875	22.23	LL-3	.88	22.2	.775	19.7	2.8	.50	.53	13	1.5	6.6	.35	8.9	0.050	1.3	7.00	SST	CG	N
0.875	22.23	S-1698	.88	22.2	.705	17.9	88	15	.25	6.5	22	100	.30	7.6	0.085	2.2	3.50	SST	CG	N
0.875	22.23	26	.88	22.2	.693	17.6	88	15	.32	8.2	28	125	.49	12.3	0.091	2.3	4.33	HD	C	Z
0.875	22.23	S-886	.94	23.8	.793	20.1	4.1	.71	.72	18	2.9	13	.18	4.7	0.041	1.0	3.50	SST	C	N
0.875	22.23	10315	.94	23.8	.751	19.1	26	4.6	.38	9.6	9.9	44	.28	7.1	0.062	1.6	3.50	SPR	C	Z
0.875	22.23	4184	1.00	25.4	.675	17.1	77	14	.40	10	31	137	.60	15.2	0.100	2.5	6.00	SPR	CG	Z
0.875	22.23	12133	1.03	26.2	.757	19.2	16	2.8	.53	14	8.6	38	.24	6.0	0.059	1.5	4.00	SPR	CG	Z
0.875	22.23	3686	1.06	27.0	.715	18.2	59	10	.34	8.7	20	89	.32	8.1	0.080	2.0	4.00	SPR	CG	Z
0.875	22.23	S-1437	1.09	27.8	.665	16.9	111	19	.36	9.1	40	177	.53	13.3	0.105	2.7	5.00	SST	CG	N
0.875	22.23	GG-53	1.13	28.6	.655	16.6	157	27	.30	7.7	47	211	.55	14.0	0.110	2.8	5.00	SPR	CG	Z
0.875	22.23	11118	1.16	29.4	.799	20.3	1.4	.24	.90	23	1.2	5.5	.26	6.5	0.038	1.0	5.75	MW	C	N
0.875	22.23	H-37	1.25	31.8	.785	19.9	1.2	.22	.74	19	.92	4.1	.51	13.0	0.045	1.1	10.3	MW	C	N
0.875	22.23	S-127	1.28	32.5	.775	19.7	2.5	.44	.90	22.8	2.28	10.1	.38	9.5	0.050	1.3	7.50	SST	CG	N
0.875	22.23	10307	1.31	33.3	.715	18.2	23	4.1	.75	19	18	78	.56	14.2	0.080	2.0	7.00	SPR	CG	Z
0.875	22.23	S-1446	1.38	34.9	.751	19.1	8.6	1.5	1.0	25	8.6	38	.37	9.4	0.062	1.6	6.00	SST	CG	N
0.875	22.23	11263	1.38	34.9	.693	17.6	32	5.5	.67	17	21	94	.71	17.9	0.091	2.3	7.75	SST	CG	N
0.875	22.23	914	1.38	34.9	.665	16.9	96	17	.45	11	43	190	.74	18.7	0.105	2.7	6.00	HD	C	Z
0.875	22.23	3167	1.44	36.5	.615	15.6	221	39	.34	8.6	75	334	.85	21.5	0.130	3.3	6.50	SPR	CG	Z
0.875	22.23	S-1359	1.50	38.1	.813	20.7	.96	.17	1.3	34	1.3	5.7	.16	3.9	0.031	0.8	4.00	SST	C	N
0.875	22.23	11550	1.50	38.1	.789	20.0	2.8	.50	1.2	32	3.5	16	.26	6.6	0.043	1.1	5.00	SPR	C	Z
0.875	22.23	10497	1.50	38.1	.731	18.6	12	2.1	.91	23	11	48	.59	15.1	0.072	1.8	8.25	SPR	CG	Z
0.875	22.23	10398	1.50	38.1	.715	18.2	18	3.2	.82	21	15	66	.68	17.3	0.080	2.0	8.50	SPR	CG	Z
0.875	22.23	4389	1.56	39.7	.731	18.6	10	1.8	.90	23	9.2	41	.67	16.9	0.072	1.8	9.25	SPR	CG	Z
0.875	22.23	S-1574	1.59	40.5	.775	19.7	3.5	.62	1.2	32	4.4	20	.35	8.9	0.050	1.3	6.00	SST	C	N
0.875	22.23	S-208	1.63	41.3	.751	19.1	6.9	1.2	1.2	30	8.2	36	.43	11.0	0.062	1.6	7.00	SST	CG	N
0.875	22.23	S-42	1.63	41.3	.727	18.5	15	2.6	1.0	25	15	66	.52	13.2	0.074	1.9	7.00	SST	CG	N
0.875	22.23	11584	1.75	44.5	.733	18.6	9.4	1.6	1.0	26	9.4	42	.75	18.9	0.071	1.8	9.50	SPR	CG	Z
0.875	22.23	11999	1.78	45.2	.665	16.9	70	12	.62	16	43	190	.79	20.0	0.105	2.7	7.50	SPR	CG	Z
0.875	22.23	S-1390	1.88	47.6	.715	18.2	17	3.0	1.1	28	19	83	.72	18.3	0.080	2.0	8.00	SST	C	N
0.875	22.23	3525	1.88	47.6	.491	12.5	943	165	.22	5.7	212	943	1.63	41.5	0.192	4.9	8.50	HD	CG	Z
0.875	22.23	B7-52	1.91	48.4	.643	16.3	64	11	.72	18	46	204	1.19	30.2	0.116	2.9	10.3	SST	CG	N
0.875	22.23	2588	1.94	49.2	.693	17.6	41	7.2	.69	17	28	125	.64	16.2	0.091	2.3	7.00	HD	CG	Z
0.875	22.23	A13-70	1.97	50.0	.731	18.6	15	2.6	.94	24	14	61	.54	13.7	0.072	1.8	6.50	SST	C	N
0.875	22.23	12264	2.00	50.8	.749	19.0	11	1.9	.98	25	10	46	.44	11.2	0.063	1.6	6.00	SPR	C	Z
0.875	22.23	1916	2.00	50.8	.731	18.6	16	2.8	.92	23	15	65	.55	14.0	0.072	1.8	6.67	SPR	C	Z
0.875	22.23	II-65	2.00	50.8	.695	17.7	32	5.7	.84	21	27	121	.81	20.6	0.090	2.3	8.00	SPR	C	Z
0.875	22.23	3308	2.00	50.8	.691	17.6	61	11	.47	12	29	129	.60	15.2	0.092	2.3	5.50	SPR	C	Z
0.875	22.23	3926	2.00	50.8	.665	16.9	77	13	.56	14	43	190	.84	21.3	0.105	2.7	7.00	SPR	C	Z
0.875	22.23	68	2.00	50.8	.635	16.1	99	17	.62	16	61	272	1.08	27.4	0.120	3.0	9.00	HD	CG	Z
0.875	22.23	808	2.00	50.8	.521	13.2	572	100	.31	7.9	177	787	1.64	41.6	0.177	4.5	9.25	HD	CG	Z
0.875	22.23	2825	2.03	51.6	.631	16.0	76	13	.58	15	44	196	1.45	36.8	0.122	3.1	12.0	SPR	CG	GI
0.875	22.23	10552	2.06	52.4	.765	19.4	4.3	.76	1.6	40	6.9	31	.47	11.9	0.055	1.4	7.50	SPR	C	Z
0.875	22.23	11841	2.06	52.4	.667	16.9	46	8.0	.91	23	42	185	1.04	26.4	0.104	2.6	10.0	SPR	CG	Z
0.875	22.23	12449	2.06	52.4	.633	16.1	120	21	.52	13	63	279	.97	24.6	0.121	3.1	8.00	SPR	CG	N
0.875	22.23	11205	2.13	54.0	.745	18.9	5.4	.94	1.4	36	7.5	34	.72	18.2	0.065	1.7	10.0	SST	C	N
0.875	22.23	3025	2.13	54.0	.625	15.9	139	24	.50	13	69	307	1.13	28.6	0.125	3.2	8.00	SPR	C	Z
0.875	22.23	A14-66	2.16	54.8	.741	18.8	12	2.1	.97	25	12	52	.40	10.2	0.067	1.7	6.00	SST	CG	N
0.875	22.23	2971	2.19	55.6	.691	17.6	48	8.3	.61	15	29	129	.69	17.5	0.092	2.3	6.50	SPR	C	Z
0.875	22.23	12005	2.19	55.6	.689	17.5	45	7.9	.67	17	30	133	.65	16.5	0.093	2.4	7.00	SPR	CG	Z
0.875	22.23	S-299	2.22	56.4	.795	20.2	.92	.16	1.9	47	1.7	7.6	.36	9.1	0.040	1.0	8.00	SST	C	N
0.875	22.23	11104	2.25	57.2	.761	19.3	5.0	.88	1.5	39	7.7	34	.48	12.3	0.057	1.4	7.50	SPR	C	N
0.875	22.23	3895	2.25	57.2	.725	18.4	11	1.9	1.5	38	17	74	.75	19.1	0.075	1.9	10.0	SPR	CG	Z
0.875	22.23	10119	2.25	57.2	.649	16.5	59	10	.87	22	51	228	1.24	31.6	0.113	2.9	11.0	SPR	CG	Z
0.875	22.23	2927	2.38	60.3	.767	19.5	2.2	.39	1.7	44	3.9	17	.64	16.3	0.054	1.4	12.0	SPR	CG	GI
0.875	22.23	3952	2.38	60.3	.731	18.6	11	1.9	1.4	35	15	65	.72	18.3	0.072	1.8	9.00	SPR	C	Z
0.875	22.23	S-1314	2.44	61.9	.665	16.9	35	6.1	1.1	29	40	177	1.21	30.7	0.105	2.7	11.5	SST	CG	N
0.875	22.23	11272	2.50	63.5	.665	16.9	59	10	.73	18	43	190	.89	22.7	0.105	2.7	8.50	SPR	CG	Z
0.875	22.23	864	2.50	63.5	.635	16.1	69	12	.88	22	61	272	1.44	36.6	0.120	3.0	12.0	HD	CG	Z
0.875	22.23	49	2.50	63.5	.605	15.4	118	21	.71	18	84	372	1.62	41.1	0.135	3.4	12.0	HD	CG	Z
0.875	22.23	4142	2.75	69.9	.663	16.8	47	8.2	.94	24	44	196	1.11	28.3	0.106	2.7	10.5	SPR	CG	Z



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	F S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.875	22.23	10808	4.00	101.6	.731	18.6	6.8	1.2	2.2	55	15	65	1.01	25.6	0.072	1.8	13.0	SPR	C	Z
0.875	22.23	2711	4.00	101.6	.715	18.2	8.4	1.5	2.4	61	20	89	1.52	38.5	0.080	2.0	17.5	SPR	C	Z
0.875	22.23	2808	4.00	101.6	.715	18.2	7.5	1.3	2.5	64	19	84	1.49	37.8	0.080	2.0	17.8	HD	C	Z
0.875	22.23	891	4.00	101.6	.715	18.2	9.0	1.6	2.2	56	20	89	1.28	32.5	0.080	2.0	15.0	HD	C	Z
0.875	22.23	S-460	4.00	101.6	.691	17.6	16	2.8	1.7	43	27	120	1.36	34.5	0.092	2.3	13.8	SST	C	N
0.875	22.23	3279	4.00	101.6	.685	17.4	18	3.1	1.8	46	32	142	1.62	41.0	0.095	2.4	16.0	SPR	C	Z
0.875	22.23	4253	4.00	101.6	.665	16.9	27	4.7	1.6	40	43	190	1.81	46.0	0.105	2.7	16.3	SPR	C	Z
0.875	22.23	12797	4.31	109.5	.625	15.9	50	8.8	1.9	49	96	428	2.33	59.1	0.125	3.2	18.6	MW	CG	N
0.875	22.23	11151	4.41	111.9	.625	15.9	58	10	1.2	30	69	307	2.16	54.8	0.125	3.2	16.0	HD	C	Z
0.875	22.23	2826	4.50	114.3	.675	17.1	17	3.0	2.5	64	43	193	1.99	50.5	0.100	2.5	20.0	MW	CG	GI
0.875	22.23	653	4.50	114.3	.521	13.2	227	40	.78	20	177	787	3.58	91.0	0.177	4.5	20.3	HD	CG	Z
0.875	22.23	2732	4.94	125.4	.691	17.6	15	2.6	2.0	50	29	129	1.52	38.6	0.092	2.3	16.5	SPR	CG	Z
0.875	22.23	3933	5.50	139.7	.693	17.6	12	2.1	2.3	59	28	125	1.73	43.9	0.091	2.3	19.0	SPR	CG	Z
0.875	22.23	11973	5.63	142.9	.675	17.1	16	2.8	3.2	81	52	231	2.10	53.3	0.100	2.5	21.0	MW	CG	Z
0.875	22.23	883	6.00	152.4	.693	17.6	9.3	1.6	3.0	77	28	125	2.18	55.5	0.091	2.3	24.0	HD	CG	Z
0.875	22.23	872	6.00	152.4	.665	16.9	16	2.8	2.7	67	43	190	2.81	71.3	0.105	2.7	25.8	HD	C	Z
0.875	22.23	865	6.00	152.4	.635	16.1	29	5.1	2.1	54	61	272	3.12	79.2	0.120	3.0	26.0	HD	CG	Z
0.875	22.23	855	6.00	152.4	.605	15.4	46	8.0	1.8	46	84	372	3.75	95.2	0.135	3.4	27.8	HD	CG	Z
0.875	22.23	818	6.00	152.4	.579	14.7	70	12	1.6	40	109	485	4.11	104.3	0.148	3.8	27.8	HD	CG	Z
0.875	22.23	1939	6.50	165.1	.689	17.5	7.6	1.3	3.5	88	27	118	3.02	76.8	0.093	2.4	31.5	SPR	C	Z
0.875	22.23	395	7.13	181.0	.647	16.4	20	3.5	2.7	68	53	234	3.41	86.7	0.114	2.9	30.0	SPR	CG	Z
0.875	22.23	892	7.75	196.9	.715	18.2	4.5	.79	4.4	113	20	89	2.32	58.9	0.080	2.0	28.0	HD	C	Z
0.875	22.23	11686	7.75	196.9	.661	16.8	13	2.2	3.6	92	45	201	3.88	98.5	0.107	2.7	35.3	SPR	C	Z
0.875	22.23	11982	8.22	208.8	.671	17.0	10	1.8	3.9	98	39	175	3.57	90.7	0.102	2.6	35.0	SPR	CG	Z
0.875	22.23	11525	8.28	210.3	.685	17.4	12	2.1	2.7	69	32	142	2.28	57.9	0.095	2.4	23.0	SPR	CG	Z
0.875	22.23	377	8.50	215.9	.731	18.6	3.7	.65	3.9	100	15	65	1.66	42.1	0.072	1.8	22.0	HD	C	Z
0.875	22.23	10004	8.88	225.4	.635	16.1	18	3.2	3.4	85	61	272	4.80	121.9	0.120	3.0	40.0	SPR	CG	Z
0.875	22.23	289	12.0	304.8	.751	19.1	1.2	.22	8.0	204	9.9	44	2.17	55.1	0.062	1.6	34.0	HD	C	Z
0.875	22.23	899	12.0	304.8	.731	18.6	2.1	.36	7.1	181	15	65	2.83	71.8	0.072	1.8	38.3	HD	C	Z
0.875	22.23	893	12.0	304.8	.715	18.2	2.9	.50	7.0	177	20	89	3.49	88.7	0.080	2.0	42.7	HD	C	Z
0.875	22.23	10677	12.3	311.2	.645	16.4	11	1.9	5.0	127	54	240	6.33	160.7	0.115	2.9	55.0	SPR	CG	Z
0.875	22.23	4015	18.5	469.9	.715	18.2	1.9	.33	11	272	20	89	5.24	133.1	0.080	2.0	64.5	HD	C	Z
0.875	22.23	4037	26.5	673.1	.605	15.4	10	1.8	8.2	207	84	372	15.8	401.2	0.135	3.4	117.0	SPR	CG	Z
0.890	22.61	2827	.63	15.9	.730	18.5	37	6.5	.23	5.7	8.3	37	.40	10.2	0.080	2.0	5.00	HD	CG	Z
0.890	22.61	AA-64	.63	15.9	.630	16.0	468	82	.11	2.7	49	218	.52	13.2	0.130	3.3	4.00	SPR	CG	Z
0.890	22.61	10584	.91	23.0	.650	16.5	261	46	.23	5.9	60	268	.54	13.7	0.120	3.0	4.50	SPR	CG	Z
0.890	22.61	10031	1.00	25.4	.796	20.2	2.9	.51	.67	17	2.0	8.7	.33	8.4	0.047	1.2	6.00	SPR	C	Z
0.890	22.61	1910	1.00	25.4	.780	19.8	11	2.0	.61	15	6.8	30	.22	5.6	0.055	1.4	4.00	SPR	CG	Z
0.890	22.61	11919	1.09	27.8	.682	17.3	102	18	.37	9.4	38	169	.52	13.2	0.104	2.6	5.00	SST	CG	N
0.890	22.61	PP-64	1.38	34.9	.770	19.6	8.1	1.4	1.0	26	8.3	37	.36	9.1	0.060	1.5	6.00	SPR	CG	N
0.890	22.61	11232	1.38	34.9	.748	19.0	11	1.9	.81	20	8.9	40	.57	14.4	0.071	1.8	8.00	SPR	CG	N
0.890	22.61	3383	1.38	34.9	.736	18.7	34	6.0	.52	13	18	78	.44	11.2	0.077	2.0	4.75	SPR	C	Z
0.890	22.61	11412	1.38	34.9	.680	17.3	90	16	.47	12	42	187	.63	16.0	0.105	2.7	6.00	SPR	CG	Z
0.890	22.61	S-324	1.38	34.9	.566	14.4	595	104	.20	5.1	121	536	.93	23.7	0.162	4.1	5.75	SST	CG	N
0.890	22.61	11863	1.41	35.7	.768	19.5	5.0	.87	.80	20	4.0	18	.61	15.5	0.061	1.5	9.00	SPR	C	N
0.890	22.61	10293	1.44	36.5	.746	18.9	14	2.5	.93	24	13	59	.50	12.8	0.072	1.8	7.00	SPR	CG	Z
0.890	22.61	10165	1.44	36.5	.578	14.7	431	75	.28	7.2	122	542	1.09	27.7	0.156	4.0	7.00	SPR	CG	Z
0.890	22.61	A14-54	1.50	38.1	.806	20.5	1.8	.32	1.2	32	2.3	10	.25	6.4	0.042	1.1	6.00	SPR	CG	N
0.890	22.61	11318	1.50	38.1	.748	19.0	13	2.2	.99	25	12	56	.51	13.1	0.071	1.8	7.25	SPR	CG	Z
0.890	22.61	10338	1.50	38.1	.730	18.5	18	3.1	.84	21	15	66	.66	16.8	0.080	2.0	8.25	SPR	CG	Z
0.890	22.61	11171	1.50	38.1	.730	18.5	20	3.5	.90	23	18	81	.60	15.2	0.080	2.0	7.50	SPR	CG	Z
0.890	22.61	WW-66	1.63	41.3	.786	20.0	2.2	.39	1.1	28	2.5	11	.52	13.2	0.052	1.3	9.00	SST	C	N
0.890	22.61	10656	1.63	41.3	.750	19.1	10	1.8	1.0	27	10	47	.58	14.7	0.070	1.8	8.25	SPR	CG	Z
0.890	22.61	10488	1.69	42.8	.626	15.9	154	27	.50	13	77	343	1.12	28.5	0.132	3.4	8.50	SPR	CG	Z
0.890	22.61	12175	1.78	45.2	.620	15.7	185	32	.45	11	82	367	1.08	27.4	0.135	3.4	8.00	SPR	CG	N
0.890	22.61	00-88	1.88	47.6	.658	16.7	57	10	.66	17	38	168	1.22	30.9	0.116	2.9	10.5	SST	CG	N
0.890	22.61																			



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.890	22.61	11962	5.56	141.3	.688	17.5	16	2.8	2.3	60	38	167	2.12	53.9	0.101	2.6	21.0	SPR	CG	Z
0.890	22.61	11764	6.00	152.4	.620	15.7	43	7.5	1.9	49	82	367	3.75	95.2	0.135	3.4	27.8	SPR	CG	Z
0.890	22.61	12395	6.13	155.6	.650	16.5	27	4.8	2.2	56	60	268	3.24	82.3	0.120	3.0	26.0	SPR	C	Z
0.890	22.61	12604	6.88	174.6	.578	14.7	82	14	2.1	53	171	759	4.56	115.9	0.156	4.0	28.3	MW	C	N
0.906	23.01	2766	.50	12.7	.686	17.4	417	73	.11	2.8	46	205	.33	8.4	0.110	2.8	3.00	SPR	CG	Z
0.906	23.01	1777	.59	15.1	.782	19.9	11	1.9	.21	5.2	2.2	9.9	.39	9.9	0.062	1.6	5.25	HD	C	Z
0.906	23.01	3542	.59	15.1	.780	19.8	19	3.3	.34	8.7	6.4	29	.25	6.4	0.063	1.6	4.00	HD	CG	Z
0.906	23.01	12410	.63	15.9	.798	20.3	20	3.5	.32	8.2	6.4	28	.22	5.5	0.054	1.4	3.00	SPR	C	N
0.906	23.01	10008	.63	15.9	.782	19.9	35	6.2	.27	6.9	9.6	43	.19	4.7	0.062	1.6	3.00	SPR	CG	Z
0.906	23.01	10118	.63	15.9	.782	19.9	18	3.1	.32	8.0	5.6	25	.31	7.9	0.062	1.6	4.00	HD	C	Z
0.906	23.01	2954	.75	19.1	.786	20.0	15	2.7	.51	13	7.8	35	.24	6.1	0.060	1.5	4.00	SPR	CG	Z
0.906	23.01	A11-51	.75	19.1	.664	16.9	340	59	.18	4.5	61	270	.47	11.9	0.121	3.1	4.00	SPR	CG	Z
0.906	23.01	10551	.81	20.6	.834	21.2	2.4	.43	.65	17	1.6	7.1	.16	4.1	0.036	0.9	3.50	SPR	C	Z
0.906	23.01	2538	.91	23.0	.656	16.7	368	65	.18	4.6	67	297	.50	12.7	0.125	3.2	4.00	SPR	CG	Z
0.906	23.01	11847	1.16	29.4	.812	20.6	4.9	.86	.86	22	4.2	19	.19	4.8	0.047	1.2	4.00	SST	CG	N
0.906	23.01	11536	1.16	29.4	.760	19.3	24	4.1	.63	16	15	66	.44	11.1	0.073	1.9	5.00	SPR	CG	Z
0.906	23.01	10390	1.22	31.0	.736	18.7	27	4.7	.62	16	17	75	.60	15.1	0.085	2.2	7.00	SPR	CG	Z
0.906	23.01	1579	1.25	31.8	.746	18.9	42	7.3	.46	12	19	86	.44	11.2	0.080	2.0	4.50	SPR	C	Z
0.906	23.01	PP-72	1.25	31.8	.746	18.9	23	4.1	.73	19	17	75	.52	13.2	0.080	2.0	6.50	SPR	CG	BO
0.906	23.01	10463	1.25	31.8	.734	18.6	25	4.3	.58	15	14	64	.67	16.9	0.086	2.2	7.75	SPR	CG	Z
0.906	23.01	11121	1.25	31.8	.724	18.4	33	5.8	.57	14	19	84	.68	17.3	0.091	2.3	7.50	HD	CG	Z
0.906	23.01	PP-45	1.28	32.5	.846	21.5	.17	.03	.89	23	.15	.69	.39	9.9	0.030	0.8	12.0	MW	C	GI
0.906	23.01	2881	1.31	33.3	.782	19.9	12	2.1	.81	21	9.6	43	.31	7.9	0.062	1.6	5.00	SPR	CG	Z
0.906	23.01	10567	1.38	34.9	.746	18.9	17	2.9	.72	18	12	53	.66	16.8	0.080	2.0	8.25	SPR	CG	Z
0.906	23.01	10397	1.47	37.3	.750	19.1	16	2.7	.84	21	13	59	.62	15.8	0.078	2.0	8.00	SPR	CG	Z
0.906	23.01	S-1546	1.50	38.1	.864	21.9	.03	.01	1.2	31	.04	.19	.28	7.1	0.021	0.5	12.3	SST	C	N
0.906	23.01	11319	1.50	38.1	.750	19.1	19	3.3	.88	22	16	73	.62	15.8	0.078	2.0	7.00	SPR	C	Z
0.906	23.01	10377	1.50	38.1	.746	18.9	16	2.8	.82	21	13	59	.68	17.3	0.080	2.0	8.50	SPR	CG	Z
0.906	23.01	10345	1.50	38.1	.736	18.7	23	4.0	.74	19	17	74	.77	19.4	0.085	2.2	8.00	SPR	C	Z
0.906	23.01	S-1196	1.50	38.1	.696	17.7	49	8.6	.66	17	33	145	.84	21.3	0.105	2.7	8.00	SST	CG	N
0.906	23.01	B17-187	1.53	38.9	.734	18.6	29	5.0	.84	21	24	107	.60	15.3	0.086	2.2	7.00	SPR	CG	Z
0.906	23.01	10674	1.56	39.7	.766	19.5	9.8	1.7	.93	24	9.2	41	.63	16.0	0.070	1.8	8.00	SPR	C	Z
0.906	23.01	10842	1.56	39.7	.746	18.9	20	3.5	.90	23	18	80	.66	16.8	0.080	2.0	7.25	SPR	C	N
0.906	23.01	3149	1.56	39.7	.666	16.9	112	20	.53	13	59	264	.90	22.9	0.120	3.0	7.50	SPR	CG	Z
0.906	23.01	3754	1.75	44.5	.696	17.7	68	12	.61	15	41	184	.74	18.7	0.105	2.7	7.00	HD	CG	Z
0.906	23.01	11941	1.75	44.5	.636	16.2	174	30	.47	12	81	361	1.08	27.4	0.135	3.4	8.00	SPR	CG	Z
0.906	23.01	1603	2.13	54.0	.810	20.6	1.1	.19	1.5	38	1.6	7.3	.62	15.8	0.048	1.2	13.0	MW	CG	Z
0.906	23.01	10739	2.25	57.2	.790	20.1	4.9	.85	1.6	41	7.9	35	.49	12.5	0.058	1.5	7.50	SPR	C	N
0.906	23.01	10614	2.31	58.7	.746	18.9	12	2.0	1.4	36	17	74	.88	22.4	0.080	2.0	11.0	SPR	CG	Z
0.906	23.01	11924	2.34	59.5	.746	18.9	16	2.8	1.2	31	19	86	.68	17.3	0.080	2.0	8.50	SPR	CG	Z
0.906	23.01	11853	2.38	60.3	.840	21.3	.65	.11	2.2	55	1.4	6.2	.21	5.4	0.033	0.8	5.50	SST	C	N
0.906	23.01	10378	2.38	60.3	.782	19.9	2.9	.52	1.5	38	4.4	20	.87	22.0	0.062	1.6	14.0	SPR	CG	Z
0.906	23.01	12104	2.47	62.7	.550	14.0	416	73	.42	11	175	777	1.96	49.7	0.178	4.5	11.0	SPR	CG	Z
0.906	23.01	53	2.75	69.9	.696	17.7	35	6.2	1.2	30	41	184	1.33	33.8	0.105	2.7	11.7	HD	C	Z
0.906	23.01	1665	3.13	79.4	.756	19.2	8.8	1.5	2.2	57	20	87	.90	22.9	0.075	1.9	11.0	MW	C	Z
0.906	23.01	1537	3.16	80.2	.762	19.4	7.2	1.3	2.0	50	14	63	.88	22.4	0.072	1.8	11.3	SPR	C	Z
0.906	23.01	2679	3.19	81.0	.724	18.4	14	2.4	1.7	43	23	104	1.48	37.6	0.091	2.3	15.3	MW	C	Z
0.906	23.01	3463	3.38	85.7	.722	18.3	20	3.5	1.4	36	28	125	1.15	29.2	0.092	2.3	11.5	HD	C	Z
0.906	23.01	B9-55	3.50	88.9	.826	21.0	.52	.09	3.0	76	1.5	6.8	.52	13.2	0.040	1.0	13.0	SPR	CG	N
0.906	23.01	3233	3.56	90.5	.714	18.1	19	3.3	1.7	43	32	142	1.46	37.2	0.096	2.4	14.3	SPR	C	Z
0.906	23.01	12109	3.59	91.3	.760	19.3	8.8	1.5	1.7	43	15	66	.73	18.5	0.073	1.9	10.0	SPR	CG	Z
0.906	23.01	S-3042	3.63	92.1	.610	15.5	115	20	.83	21	95	424	2.07	52.6	0.148	3.8	14.0	SST	CG	N
0.906	23.01	3342	4.00	101.6	.756	19.2	3.7	.65	2.2	57	8.2	37	1.76	44.8	0.075	1.9	23.5	SPR	CG	Z
0.906	23.01	3435	4.25	108.0	.806	20.5	1.4	.25	3.5	90	5.1	23	.65	16.5	0.050	1.3	12.0	SPR	C	Z
0.906	23.01	1689	5.00	127.0	.746	18.9	7.1	1.2	2.7	70	19	86	1.34	34.0	0.080	2.0	16.8	SPR	CG	Z
0.906	23.01	12677	5.38	136.5	.656	16.7	35	6.1	1.9	48	67	297	3.00	76.2	0.125	3.2	23.0	SPR	C	N
0.906	23.01	12158	8.75	222.3	.756	19.2	2.5	.43	6.2	157	15	68	2.55	64.8	0.075	1.9	34.0	SPR	CG	Z
0.906	23.01	3912	9.0																	



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.921	23.39	S-140	1.50	38.1	.547	13.9	1104	193	.15	3.7	163	725	1.03	26.1	0.187	4.7	5.50	SST	CG	N
0.921	23.39	10254	1.56	39.7	.771	19.6	33	5.8	.47	12	16	70	.32	8.1	0.075	1.9	4.25	SPR	CG	Z
0.921	23.39	10610	1.56	39.7	.703	17.9	79	14	.53	14	42	188	.68	17.3	0.109	2.8	6.25	SST	CG	N
0.921	23.39	3189	1.59	40.5	.761	19.3	15	2.7	.91	23	14	62	.68	17.3	0.080	2.0	8.50	SPR	CG	GI
0.921	23.39	11207	1.69	42.8	.721	18.3	58	10	.57	14	33	146	.60	15.2	0.100	2.5	6.00	SST	CG	N
0.921	23.39	3815	1.75	44.5	.661	16.8	166	29	.43	11	72	319	.91	23.1	0.130	3.3	7.00	SPR	CG	Z
0.921	23.39	PP-1	2.03	51.6	.621	15.8	244	43	.43	11	106	470	1.28	32.4	0.150	3.8	8.50	SPR	CG	Z
0.921	23.39	11637	2.06	52.4	.799	20.3	4.5	.78	1.5	38	6.8	30	.55	13.9	0.061	1.5	9.00	SPR	CG	Z
0.921	23.39	11236	2.38	60.3	.797	20.2	2.8	.49	1.5	38	4.2	19	.87	22.0	0.062	1.6	14.0	SPR	CG	Z
0.921	23.39	1737	2.75	69.9	.665	16.9	72	13	.98	25	70	313	1.63	41.5	0.128	3.3	12.8	HD	CG	Z
0.921	23.39	S-1611	2.78	70.6	.731	18.6	17	2.9	1.5	39	26	115	1.24	31.4	0.095	2.4	13.0	SST	CG	N
0.921	23.39	10597	3.00	76.2	.777	19.7	7.0	1.2	2.0	51	14	62	.86	21.9	0.072	1.8	11.0	SPR	C	Z
0.921	23.39	3351	3.00	76.2	.761	19.3	9.9	1.7	1.9	49	19	85	.96	24.4	0.080	2.0	12.0	HD	CG	Z
0.921	23.39	3070	3.00	76.2	.671	17.0	75	13	.87	22	66	293	1.41	35.7	0.125	3.2	11.3	SPR	CG	GI
0.921	23.39	MM-92	3.00	76.2	.541	13.7	505	88	.39	10	198	880	2.19	55.5	0.190	4.8	11.5	SPR	CG	N
0.921	23.39	12103	3.22	81.8	.821	20.9	1.5	.26	2.7	68	4.0	18	.55	14.0	0.050	1.3	11.0	SPR	CG	Z
0.921	23.39	1888	3.31	84.1	.777	19.7	7.0	1.2	2.0	51	14	62	.86	21.9	0.072	1.8	11.0	HD	C	Z
0.921	23.39	1685	4.50	114.3	.711	18.1	25	4.3	1.7	42	41	182	1.68	42.7	0.105	2.7	15.0	SPR	C	Z
0.921	23.39	12174	4.75	120.7	.711	18.1	21	3.8	1.9	48	41	182	1.79	45.3	0.105	2.7	17.0	SPR	CG	Z
0.921	23.39	12040	5.50	139.7	.791	20.1	2.0	.36	4.1	103	8.3	37	1.43	36.3	0.065	1.7	22.0	SPR	CG	Z
0.921	23.39	S-462	6.25	158.8	.777	19.7	3.7	.65	3.5	89	13	58	1.28	32.5	0.072	1.8	16.8	SST	C	N
0.921	23.39	3285	6.50	165.1	.701	17.8	19	3.3	2.4	61	45	201	2.53	64.3	0.110	2.8	23.0	SPR	CG	Z
0.921	23.39	4017	19.8	501.7	.631	16.0	20	3.5	5.0	126	98	437	10.2	259.7	0.145	3.7	70.5	SPR	CG	Z
0.938	23.83	3663	.44	11.1	.828	21.0	19	3.3	.27	6.9	5.2	23	.17	4.2	0.055	1.4	3.00	SPR	CG	Z
0.938	23.83	3687	.63	15.9	.828	21.0	19	3.3	.34	8.6	6.5	29	.22	5.6	0.055	1.4	3.00	SPR	C	Z
0.938	23.83	S-3040	.75	19.1	.678	17.2	451	79	.14	3.6	63	282	.46	11.6	0.130	3.3	3.50	SST	CG	N
0.938	23.83	4235	.75	19.1	.668	17.0	615	108	.13	3.2	79	350	.47	12.0	0.135	3.4	3.50	SPR	CG	Z
0.938	23.83	MM-75	.78	19.8	.758	19.3	46	8.0	.33	8.4	15	67	.45	11.4	0.090	2.3	5.00	SST	CG	N
0.938	23.83	1855	.94	23.8	.698	17.7	218	38	.37	9.4	80	357	.54	13.7	0.120	3.0	4.50	MW	CG	Z
0.938	23.83	S-902	.94	23.8	.694	17.6	260	46	.21	5.4	55	245	.49	12.4	0.122	3.1	4.00	SST	CG	N
0.938	23.83	924	1.13	28.6	.728	18.5	86	15	.44	11	38	170	.68	17.3	0.105	2.7	5.50	HD	C	Z
0.938	23.83	11762	1.16	29.4	.622	15.8	755	132	.16	4.1	121	537	.71	18.1	0.158	4.0	4.50	SPR	CG	Z
0.938	23.83	2609	1.19	30.2	.614	15.6	605	106	.21	5.4	130	577	.89	22.6	0.162	4.1	5.50	HD	CG	Z
0.938	23.83	GG-41	1.22	31.0	.758	19.3	46	8.0	.52	13	24	105	.45	11.4	0.090	2.3	5.00	SST	CG	N
0.938	23.83	1617	1.25	31.8	.826	21.0	5.2	.90	.86	22	4.4	20	.39	10.0	0.056	1.4	6.00	SPR	C	Z
0.938	23.83	10524	1.25	31.8	.734	18.6	71	12	.52	13	37	164	.59	14.9	0.102	2.6	5.75	SPR	CG	Z
0.938	23.83	B2-59	1.25	31.8	.668	17.0	284	50	.39	9.8	110	489	.71	18.0	0.135	3.4	5.25	MW	CG	N
0.938	23.83	10211	1.38	34.9	.814	20.7	9.0	1.6	1.0	26	9.3	41	.34	8.7	0.062	1.6	5.50	SPR	CG	Z
0.938	23.83	10268	1.38	34.9	.814	20.7	11	1.8	.88	22	9.3	41	.37	9.4	0.062	1.6	5.00	SPR	C	N
0.938	23.83	S-1123	1.38	34.9	.768	19.5	26	4.6	.78	20	21	91	.60	15.1	0.085	2.2	6.00	SST	C	N
0.938	23.83	11794	1.38	34.9	.700	17.8	105	18	.53	14	56	249	.83	21.2	0.119	3.0	7.00	SPR	CG	Z
0.938	23.83	11738	1.38	34.9	.666	16.9	318	56	.25	6.4	80	357	.68	17.3	0.136	3.5	5.00	SPR	CG	Z
0.938	23.83	11724	1.41	35.7	.754	19.2	43	7.4	.64	16	27	121	.55	14.0	0.092	2.3	6.00	SPR	CG	Z
0.938	23.83	10726	1.50	38.1	.848	21.5	.97	.17	.98	25	.96	4.3	.52	13.1	0.045	1.1	10.5	SPR	C	Z
0.938	23.83	3885	1.50	38.1	.738	18.7	54	9.5	.64	16	35	155	.65	16.5	0.100	2.5	6.50	SPR	CG	GI
0.938	23.83	10977	1.50	38.1	.728	18.5	76	13	.53	13	40	179	.63	16.0	0.105	2.7	6.00	HD	CG	Z
0.938	23.83	PP-62	1.50	38.1	.718	18.2	93	16	.48	12	45	198	.66	16.8	0.110	2.8	6.00	SPR	CG	Z
0.938	23.83	3625	1.50	38.1	.688	17.5	137	24	.66	17	90	401	.84	21.4	0.125	3.2	6.75	MW	CG	Z
0.938	23.83	CC-34	1.50	38.1	.618	15.7	355	62	.31	8.0	111	495	1.12	28.4	0.160	4.1	7.00	SST	CG	N
0.938	23.83	11149	1.59	40.5	.698	17.7	121	21	.47	12	57	255	.78	19.8	0.120	3.0	6.50	SPR	CG	Z
0.938	23.83	S-443	1.66	42.1	.838	21.3	3.8	.66	1.2	31	4.6	20	.25	6.4	0.050	1.3	5.00	SST	CG	N
0.938	23.83	828	1.75	44.5	.698	17.7	99	17	.58	15	57	255	1.02	25.9	0.120	3.0	7.50	HD	C	Z
0.938	23.83	S-940	1.78	45.2	.794	20.2	13	2.3	.98	25	13	57	.50	12.8	0.072	1.8	6.00	SST	C	N
0.938	23.83	10622	1.78	45.2	.728	18.5	54	9.4	.69	18	37	166	.74	18.7	0.105	2.7	7.00	SST	CG	N
0.938	23.83	11719	1.84	46.8	.666	16.9	191	33	.42	11	80	357	1.09	27.6	0.136	3.5	7.00	SPR	C	Z
0.938	23.83	3683	1.94	49.2	.810	20.6	5.8	1.0	1.4	36	8.1	36	.53	13.4	0.064	1.6	8.25	SPR	CG	Z
0.938	23.83	67	2.00	50.8	.778	19.8	17	3.1	1.1	27	19									



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.938	23.83	3125	4.31	109.5	.798	20.3	5.3	.92	2.4	61	13	56	.84	21.3	0.070	1.8	12.0	SPR	CG	Z
0.938	23.83	S-1407	4.38	111.1	.814	20.7	1.8	.32	3.3	84	6.1	27	1.05	26.8	0.062	1.6	17.0	SST	CG	N
0.938	23.83	3931	4.50	114.3	.626	15.9	122	21	.95	24	116	518	2.43	61.6	0.156	4.0	15.8	SPR	CG	Z
0.938	23.83	4342	5.00	127.0	.742	18.8	15	2.7	2.2	55	33	146	1.64	41.7	0.098	2.5	16.8	SPR	CG	Z
0.938	23.83	332	5.00	127.0	.584	14.8	175	31	.96	24	167	743	3.60	91.4	0.177	4.5	20.3	HD	CG	Z
0.938	23.83	2843	5.13	130.2	.764	19.4	10	1.8	2.3	59	24	107	1.31	33.1	0.087	2.2	15.0	SPR	CG	GI
0.938	23.83	S-154	5.25	133.4	.642	16.3	55	9.7	1.7	42	92	411	3.55	90.2	0.148	3.8	24.0	SST	CG	N
0.938	23.83	11627	5.25	133.4	.642	16.3	67	12	1.5	39	103	456	3.37	85.5	0.148	3.8	22.8	SPR	CG	Z
0.938	23.83	4149	6.00	152.4	.754	19.2	9.0	1.6	3.0	77	27	121	2.02	51.4	0.092	2.3	21.0	SPR	C	Z
0.938	23.83	3113	6.38	161.9	.794	20.2	4.1	.72	3.3	85	14	61	1.19	30.2	0.072	1.8	16.5	SPR	CG	Z
0.938	23.83	2569	7.25	184.2	.728	18.5	15	2.6	2.7	67	40	179	2.42	61.3	0.105	2.7	22.0	SPR	C	Z
0.938	23.83	11945	8.75	222.3	.810	20.6	1.1	.19	6.5	165	7.1	32	2.24	56.9	0.064	1.6	35.0	SPR	CG	Z
0.938	23.83	4233	9.75	247.7	.698	17.7	23	4.0	2.5	64	57	255	3.24	82.3	0.120	3.0	26.0	SPR	C	Z
0.938	23.83	3076	10.5	266.7	.756	19.2	6.8	1.2	3.9	98	26	117	2.34	59.5	0.091	2.3	25.8	SPR	CG	Z
0.938	23.83	1938	11.1	282.6	.664	16.9	29	5.0	2.9	73	82	365	5.00	127.0	0.137	3.5	36.5	SPR	CG	Z
0.953	24.21	NN-24	.69	17.4	.633	16.1	1511	265	.08	2.1	124	549	.52	13.2	0.160	4.1	3.25	SPR	CG	GI
0.953	24.21	11915	.88	22.2	.771	19.6	68	12	.35	9.0	24	107	.36	9.2	0.091	2.3	4.00	SST	CG	N
0.953	24.21	KK-68	.94	23.8	.833	21.2	6.5	1.1	.58	15	3.8	17	.36	9.1	0.060	1.5	6.00	SPR	CG	Z
0.953	24.21	3343	.94	23.8	.823	20.9	9.2	1.6	.55	14	5.0	22	.39	9.9	0.065	1.7	6.00	SPR	CG	Z
0.953	24.21	3010	.97	24.6	.771	19.6	77	13	.34	8.6	26	115	.36	9.2	0.091	2.3	4.00	SPR	CG	GI
0.953	24.21	S-1559	.98	25.0	.849	21.6	5.0	.88	.70	18	3.5	16	.29	7.3	0.052	1.3	4.50	SST	C	N
0.953	24.21	12699	1.00	25.4	.873	22.2	2.8	.49	.82	21	2.3	10	.18	4.6	0.040	1.0	3.50	SST	C	N
0.953	24.21	10683	1.00	25.4	.849	21.6	5.7	.99	.73	18	4.1	18	.27	6.9	0.052	1.3	4.25	SST	C	N
0.953	24.21	CC-72	1.00	25.4	.833	21.2	13	2.3	.63	16	8.3	37	.30	7.6	0.060	1.5	4.00	SPR	C	Z
0.953	24.21	3396	1.13	28.6	.825	21.0	12	2.2	.76	19	9.4	42	.37	9.3	0.064	1.6	4.75	SPR	C	Z
0.953	24.21	1907	1.25	31.8	.845	21.5	4.2	.74	.93	24	3.9	17	.32	8.2	0.054	1.4	6.00	SPR	CG	Z
0.953	24.21	4271	1.25	31.8	.829	21.1	7.5	1.3	.82	21	6.1	27	.43	11.0	0.062	1.6	6.00	SPR	C	Z
0.953	24.21	N-126	1.25	31.8	.797	20.2	14	2.5	.70	18	9.9	44	.55	13.9	0.078	2.0	7.00	SST	CG	N
0.953	24.21	2761	1.25	31.8	.639	16.2	433	76	.31	7.8	133	593	.94	23.9	0.157	4.0	6.00	MW	CG	Z
0.953	24.21	S-1254	1.28	32.5	.793	20.1	15	2.7	.72	18	11	49	.56	14.2	0.080	2.0	7.00	SST	CG	N
0.953	24.21	12213	1.31	33.3	.599	15.2	863	151	.19	4.9	165	733	.97	24.7	0.177	4.5	5.50	SPR	CG	GI
0.953	24.21	11385	1.41	35.7	.743	18.9	64	11	.62	16	39	175	.79	20.0	0.105	2.7	6.50	SPR	C	Z
0.953	24.21	11541	1.47	37.3	.721	18.3	137	24	.38	9.5	51	228	.73	18.4	0.116	2.9	5.25	SPR	CG	GI
0.953	24.21	S-94	1.50	38.1	.703	17.9	90	16	.50	13	45	199	1.00	25.4	0.125	3.2	8.00	SST	CG	N
0.953	24.21	B18-140	1.50	38.1	.619	15.7	430	75	.29	7.3	124	552	1.13	28.6	0.167	4.2	6.75	SST	CG	N
0.953	24.21	11856	1.63	41.3	.805	20.4	11	2.0	1.1	28	12	55	.52	13.2	0.074	1.9	7.00	SST	CG	N
0.953	24.21	3954	1.75	44.5	.809	20.5	6.6	1.2	.92	23	6.1	27	.83	21.0	0.072	1.8	10.5	SPR	C	Z
0.953	24.21	3385	1.75	44.5	.797	20.2	26	4.6	.65	16	17	76	.39	9.9	0.078	2.0	5.00	SPR	CG	Z
0.953	24.21	11492	1.75	44.5	.689	17.5	158	28	.46	12	73	323	1.06	26.8	0.132	3.4	7.00	SPR	CG	GI
0.953	24.21	2932	1.81	46.0	.739	18.8	44	7.8	.85	22	38	168	.96	24.5	0.107	2.7	9.00	SPR	CG	Z
0.953	24.21	S-984	1.91	48.4	.791	20.1	11	1.9	1.1	29	12	55	.77	19.5	0.081	2.1	9.50	SST	CG	N
0.953	24.21	AA-72	1.94	49.2	.693	17.6	98	17	.70	18	69	307	1.24	31.4	0.130	3.3	9.50	SPR	CG	Z
0.953	24.21	11157	2.00	50.8	.699	17.8	140	24	.48	12	67	297	.86	21.8	0.127	3.2	6.75	SPR	CG	Z
0.953	24.21	2875	2.13	54.0	.717	18.2	77	13	.70	18	54	240	1.09	27.7	0.118	3.0	8.25	SPR	C	Z
0.953	24.21	10566	2.28	57.9	.823	20.9	7.0	1.2	1.5	38	11	47	.54	13.6	0.065	1.7	7.25	SPR	C	Z
0.953	24.21	MM-54	2.44	61.9	.593	15.1	483	85	.29	7.5	142	633	1.44	36.6	0.180	4.6	8.00	SST	CG	N
0.953	24.21	S-1149	2.75	69.9	.793	20.1	11	1.9	1.6	40	17	77	.80	20.3	0.080	2.0	9.00	SST	C	N
0.953	24.21	11868	3.00	76.2	.783	19.9	12	2.2	1.7	43	21	92	.87	22.1	0.085	2.2	10.3	SST	CG	N
0.953	24.21	2917	3.69	93.6	.711	18.1	51	8.9	1.1	29	58	258	1.63	41.5	0.121	3.1	12.5	SPR	C	Z
0.953	24.21	2914	3.75	95.3	.793	20.1	11	1.9	1.7	42	18	82	.88	22.4	0.080	2.0	10.0	SPR	C	Z
0.953	24.21	11524	3.94	100.0	.743	18.9	23	4.0	1.7	44	40	176	1.63	41.3	0.105	2.7	14.5	SPR	CG	Z
0.953	24.21	11955	4.00	101.6	.763	19.4	19	3.2	1.6	40	29	131	1.24	31.4	0.095	2.4	12.0	SPR	C	Z
0.953	24.21	3423	4.38	111.1	.819	20.8	4.6	.81	2.5	63	12	51	.80	20.4	0.067	1.7	11.0	SPR	C	Z
0.953	24.21	3335	4.44	112.7	.693	17.6	59	10	1.2	30	69	309	2.02	51.2	0.130	3.3	14.5	SPR	C	Z
0.953	24.21	2642	4.81	122.2	.641	16.3	99	17	1.2	29	115	511	2.96	75.3	0.156	4.0	19.0	SPR	CG	Z
0.953	24.21	11558	7.75	196.9	.793	20.1	3.3	.57	5.4	136	18	78	2.40	61.0	0.080	2.0	29.0	SPR	CG	Z
0.953	24.21	3341	8.00	203.2	.539	13.7	254	45	.96	24	245	1088	5.59	142.0	0.207	5.3	27.0	SPR	CG	Z
0.968	24.59	S-182	.69																	




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.968	24.59	2952	2.34	59.5	.824	20.9	11	1.9	1.2	32	13	59	.50	12.8	0.072	1.8	7.00	SPR	CG	Z
0.968	24.59	3018	2.44	61.9	.808	20.5	11	1.8	1.6	42	17	77	.80	20.3	0.080	2.0	10.0	SPR	CG	Z
0.968	24.59	3223	2.53	64.3	.812	20.6	15	2.6	1.1	28	17	75	.62	15.8	0.078	2.0	7.00	SPR	C	Z
0.968	24.59	4272	2.63	66.7	.688	17.5	111	19	.76	19	85	378	1.51	38.2	0.140	3.6	10.8	SPR	CG	Z
0.968	24.59	A13-68	2.78	70.6	.832	21.1	7.5	1.3	1.5	38	11	50	.48	12.1	0.068	1.7	7.00	SST	CG	N
0.968	24.59	11913	2.81	71.4	.788	20.0	15	2.7	1.5	38	23	102	.90	22.9	0.090	2.3	10.0	SST	CG	N
0.968	24.59	S-429	3.06	77.8	.780	19.8	15	2.7	1.7	43	26	116	1.08	27.5	0.094	2.4	11.5	SST	CG	N
0.968	24.59	B17-176	3.28	83.3	.718	18.2	42	7.4	1.4	35	57	255	1.79	45.5	0.125	3.2	14.3	SST	CG	N
0.968	24.59	3175	3.38	85.7	.878	22.3	.94	.16	2.9	74	2.7	12	.45	11.4	0.045	1.1	10.0	SPR	CG	Z
0.968	24.59	11436	3.38	85.7	.728	18.5	47	8.2	1.2	30	56	248	1.50	38.1	0.120	3.0	12.5	SPR	CG	Z
0.968	24.59	3106	3.38	85.7	.698	17.7	83	14	.92	23	76	340	1.62	41.1	0.135	3.4	12.0	SPR	CG	Z
0.968	24.59	1661	3.50	88.9	.758	19.3	30	5.3	1.3	33	39	173	1.26	32.0	0.105	2.7	11.0	SPR	C	Z
0.968	24.59	11486	4.09	104.0	.808	20.5	8.4	1.5	2.2	55	18	81	1.04	26.4	0.080	2.0	12.0	SPR	CG	Z
0.968	24.59	11640	4.38	111.1	.808	20.5	5.6	.98	3.0	77	17	75	1.36	34.5	0.080	2.0	17.0	SPR	CG	Z
0.968	24.59	10655	4.56	115.9	.720	18.3	49	8.6	1.2	32	61	273	1.67	42.5	0.124	3.1	13.5	SPR	CG	Z
0.968	24.59	11563	7.25	184.2	.778	19.8	7.7	1.3	3.8	96	29	129	2.47	62.7	0.095	2.4	25.0	SPR	CG	Z
0.968	24.59	12457	12.0	304.8	.728	18.5	14	2.4	4.1	103	56	248	4.38	111.3	0.120	3.0	35.5	SPR	CG	Z
0.968	24.59	3065	15.3	387.4	.758	19.3	5.8	1.0	6.7	171	39	173	5.15	130.7	0.105	2.7	49.0	SPR	CG	GI
0.968	24.59	3077	16.1	409.6	.808	20.5	2.0	.34	9.3	236	18	81	3.60	91.4	0.080	2.0	45.0	SPR	CG	Z
0.975	24.77	72327	.75	19.1	.849	21.6	26	4.5	.51	13	13	58	.20	5.0	0.063	1.6	3.13	MW	CG	N
0.975	24.77	72327S	.75	19.1	.849	21.6	22	3.8	.40	10	8.8	39	.20	5.0	0.063	1.6	3.13	SST	CG	N
0.975	24.77	72339	.75	19.1	.831	21.1	40	6.9	.47	12	18	82	.24	6.2	0.072	1.8	3.38	MW	CG	N
0.975	24.77	72339S	.75	19.1	.831	21.1	34	5.9	.37	9.4	12	55	.24	6.2	0.072	1.8	3.38	SST	CG	N
0.975	24.77	72351	.75	19.1	.827	21.0	40	7.0	.49	12	20	87	.26	6.6	0.074	1.9	3.50	MW	CG	N
0.975	24.77	72351S	.75	19.1	.827	21.0	34	5.9	.40	10	13	60	.26	6.6	0.074	1.9	3.50	SST	CG	N
0.975	24.77	72367	.75	19.1	.813	20.7	61	11	.43	11	26	117	.27	6.9	0.081	2.1	3.38	MW	CG	N
0.975	24.77	72367S	.75	19.1	.813	20.7	51	9.0	.34	8.7	18	78	.27	6.9	0.081	2.1	3.38	SST	CG	N
0.975	24.77	72352	.88	22.4	.827	21.0	33	5.8	.60	15	20	88	.28	7.0	0.074	1.9	3.75	MW	CG	N
0.975	24.77	72352S	.88	22.4	.827	21.0	28	4.9	.48	12	13	60	.28	7.0	0.074	1.9	3.75	SST	CG	N
0.975	24.77	72379	.88	22.4	.805	20.4	54	9.4	.54	14	29	129	.34	8.6	0.085	2.2	4.00	MW	CG	N
0.975	24.77	72379S	.88	22.4	.805	20.4	46	8.0	.44	11	20	90	.34	8.6	0.085	2.2	4.00	SST	CG	N
0.975	24.77	72394	.88	22.4	.791	20.1	72	13	.50	13	36	160	.38	9.6	0.092	2.3	4.13	MW	CG	N
0.975	24.77	72394S	.88	22.4	.791	20.1	61	11	.40	10	24	108	.38	9.6	0.092	2.3	4.13	SST	CG	N
0.975	24.77	72403	.88	22.4	.783	19.9	85	15	.48	12	41	182	.40	10.1	0.096	2.4	4.13	MW	CG	N
0.975	24.77	72403S	.88	22.4	.783	19.9	72	13	.38	9.7	28	123	.40	10.1	0.096	2.4	4.13	SST	CG	N
0.975	24.77	72415	.88	22.4	.765	19.4	119	21	.43	11	52	230	.45	11.3	0.105	2.7	4.25	MW	CG	N
0.975	24.77	72415S	.88	22.4	.765	19.4	101	18	.35	9.0	36	160	.45	11.3	0.105	2.7	4.25	SST	CG	N
0.975	24.77	72427	.88	22.4	.751	19.1	155	27	.40	10	62	278	.48	12.1	0.112	2.8	4.25	MW	CG	N
0.975	24.77	72427S	.88	22.4	.751	19.1	131	23	.31	8.0	41	184	.48	12.1	0.112	2.8	4.25	SST	CG	N
0.975	24.77	72455	.88	22.4	.725	18.4	247	43	.33	8.5	82	365	.55	13.9	0.125	3.2	4.38	MW	CG	N
0.975	24.77	72455S	.88	22.4	.725	18.4	210	37	.27	6.9	57	253	.55	13.9	0.125	3.2	4.38	SST	CG	N
0.975	24.77	72467	.88	22.4	.705	17.9	357	62	.30	7.6	106	473	.57	14.6	0.135	3.4	4.25	MW	CG	N
0.975	24.77	72467S	.88	22.4	.705	17.9	303	53	.23	5.7	68	304	.57	14.6	0.135	3.4	4.25	SST	CG	N
0.975	24.77	72328	1.00	25.4	.849	21.6	18	3.2	.71	18	13	58	.23	5.8	0.063	1.6	3.63	MW	CG	N
0.975	24.77	72328S	1.00	25.4	.849	21.6	16	2.7	.57	14	8.8	39	.23	5.8	0.063	1.6	3.63	SST	CG	N
0.975	24.77	72340	1.00	25.4	.831	21.1	28	4.9	.66	17	18	82	.28	7.1	0.072	1.8	3.88	MW	CG	N
0.975	24.77	72340S	1.00	25.4	.831	21.1	24	4.2	.52	13	12	55	.28	7.1	0.072	1.8	3.88	SST	CG	N
0.975	24.77	72353	1.00	25.4	.827	21.0	28	4.9	.69	18	20	87	.31	7.8	0.074	1.9	4.13	MW	CG	N
0.975	24.77	72353S	1.00	25.4	.827	21.0	24	4.2	.56	14	13	60	.31	7.8	0.074	1.9	4.13	SST	CG	N
0.975	24.77	72368	1.00	25.4	.813	20.7	44	7.6	.60	15	26	117	.32	8.2	0.081	2.1	4.00	MW	CG	N
0.975	24.77	72368S	1.00	25.4	.813	20.7	37	6.5	.47	12	18	78	.32	8.2	0.081	2.1	4.00	SST	CG	N
0.975	24.77	72380	1.00	25.4	.805	20.4	52	9.0	.59	15	30	134	.35	8.9	0.085	2.2	4.13	MW	CG	N
0.975	24.77	72380S	1.00	25.4	.805	20.4	44	7.7	.46	12	20	90	.35	8.9	0.085	2.2	4.13	SST	CG	N
0.975	24.77	72395	1.00	25.4	.791	20.1	61	11	.59	15	36	159	.41	10.5	0.092	2.3	4.50	MW	CG	N
0.975	24.77	72395S	1.00	25.4	.791	20.1	52	9.1	.47	12	24	108	.41	10.5	0.092	2.3	4.50	SST	CG	N
0.975	24.77	72404	1.00	25.4	.783	19.9	74	13	.56	14	42	185	.42	10.7	0.096	2.4	4.38	MW	CG	N
0.975	24.77	72404S	1.00	25.4	.783	19.9	63	11	.44	11	28	123	.42	10.7	0.096	2.4				




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72396S	1.25	31.8	.791	20.1	40	7.0	.61	16	24	108	.48	12.3	0.092	2.3	5.25	SST	CG	N
0.975	24.77	72405	1.25	31.8	.783	19.9	56	9.9	.74	19	42	185	.49	12.5	0.096	2.4	5.13	MW	CG	N
0.975	24.77	72405S	1.25	31.8	.783	19.9	48	8.4	.57	15	28	123	.49	12.5	0.096	2.4	5.13	SST	CG	N
0.975	24.77	72417	1.25	31.8	.765	19.4	81	14	.67	17	54	241	.55	14.0	0.105	2.7	5.25	MW	CG	N
0.975	24.77	72417S	1.25	31.8	.765	19.4	69	12	.52	13	36	160	.55	14.0	0.105	2.7	5.25	SST	CG	N
0.975	24.77	72430	1.25	31.8	.751	19.1	102	18	.62	16	63	281	.62	15.6	0.112	2.8	5.50	MW	CG	N
0.975	24.77	72430S	1.25	31.8	.751	19.1	87	15	.48	12	41	184	.62	15.6	0.112	2.8	5.50	SST	CG	N
0.975	24.77	72457	1.25	31.8	.725	18.4	155	27	.55	14	85	378	.70	17.9	0.125	3.2	5.63	MW	CG	N
0.975	24.77	72457S	1.25	31.8	.725	18.4	132	23	.43	11	57	253	.70	17.9	0.125	3.2	5.63	SST	CG	N
0.975	24.77	72330	1.50	38.1	.849	21.6	12	2.0	1.1	28	13	58	.29	7.4	0.063	1.6	4.63	MW	CG	N
0.975	24.77	72330S	1.50	38.1	.849	21.6	9.9	1.7	.89	23	8.8	39	.29	7.4	0.063	1.6	4.63	SST	CG	N
0.975	24.77	72342	1.50	38.1	.831	21.1	18	3.1	1.0	27	18	82	.36	9.1	0.072	1.8	5.00	MW	CG	N
0.975	24.77	72342S	1.50	38.1	.831	21.1	15	2.6	.83	21	12	55	.36	9.1	0.072	1.8	5.00	SST	CG	N
0.975	24.77	72355	1.50	38.1	.827	21.0	18	3.1	1.1	28	20	87	.40	10.1	0.074	1.9	5.38	MW	CG	N
0.975	24.77	72355S	1.50	38.1	.827	21.0	15	2.6	.89	23	13	60	.40	10.1	0.074	1.9	5.38	SST	CG	N
0.975	24.77	72370	1.50	38.1	.813	20.7	28	4.8	.95	24	26	117	.42	10.5	0.081	2.1	5.13	MW	CG	N
0.975	24.77	72370S	1.50	38.1	.813	20.7	23	4.1	.75	19	18	78	.42	10.5	0.081	2.1	5.13	SST	CG	N
0.975	24.77	72382	1.50	38.1	.805	20.4	32	5.6	.94	24	30	134	.45	11.3	0.085	2.2	5.25	MW	CG	N
0.975	24.77	72382S	1.50	38.1	.805	20.4	27	4.8	.74	19	20	90	.45	11.3	0.085	2.2	5.25	SST	CG	N
0.975	24.77	72397	1.50	38.1	.791	20.1	38	6.6	.95	24	36	159	.55	14.0	0.092	2.3	6.00	MW	CG	N
0.975	24.77	72397S	1.50	38.1	.791	20.1	32	5.6	.76	19	24	108	.55	14.0	0.092	2.3	6.00	SST	CG	N
0.975	24.77	72406	1.50	38.1	.783	19.9	46	8.0	.91	23	42	185	.56	14.3	0.096	2.4	5.88	MW	CG	N
0.975	24.77	72406S	1.50	38.1	.783	19.9	39	6.8	.71	18	28	123	.56	14.3	0.095	2.4	5.88	SST	CG	N
0.975	24.77	72418	1.50	38.1	.765	19.4	65	11	.83	21	54	241	.63	16.0	0.105	2.7	6.00	MW	CG	N
0.975	24.77	72418S	1.50	38.1	.765	19.4	56	9.7	.65	16	36	160	.63	16.0	0.105	2.7	6.00	SST	CG	N
0.975	24.77	72431	1.50	38.1	.751	19.1	82	14	.77	20	63	281	.70	17.8	0.112	2.8	6.25	MW	CG	N
0.975	24.77	72431S	1.50	38.1	.751	19.1	70	12	.59	15	41	184	.70	17.8	0.112	2.8	6.25	SST	CG	N
0.975	24.77	72447	1.50	38.1	.735	18.7	114	20	.68	17	77	344	.75	19.1	0.120	3.0	6.25	MW	CG	N
0.975	24.77	72447S	1.50	38.1	.735	18.7	97	17	.52	13	51	225	.75	19.1	0.120	3.0	6.25	SST	CG	N
0.975	24.77	72458	1.50	38.1	.725	18.4	131	23	.66	17	87	388	.80	20.2	0.125	3.2	6.38	MW	CG	N
0.975	24.77	72458S	1.50	38.1	.725	18.4	112	20	.51	13	57	253	.80	20.2	0.125	3.2	6.38	SST	CG	N
0.975	24.77	72469	1.50	38.1	.705	17.9	177	31	.60	15	106	473	.88	22.3	0.135	3.4	6.50	MW	CG	N
0.975	24.77	72469S	1.50	38.1	.705	17.9	150	26	.45	12	68	304	.88	22.3	0.135	3.4	6.50	SST	CG	N
0.975	24.77	72476	1.50	38.1	.679	17.2	268	47	.52	13	139	617	.96	24.4	0.148	3.8	6.50	MW	CG	N
0.975	24.77	72476S	1.50	38.1	.679	17.2	228	40	.39	9.9	89	397	.96	24.4	0.148	3.8	6.50	SST	CG	N
0.975	24.77	72482	1.50	38.1	.651	16.5	415	73	.42	11	176	782	1.05	26.7	0.162	4.1	6.50	MW	CG	N
0.975	24.77	72482S	1.50	38.1	.651	16.5	353	62	.32	8.0	111	496	1.05	26.7	0.162	4.1	6.50	SST	CG	N
0.975	24.77	72331	1.75	44.5	.849	21.6	9.9	1.7	1.3	34	13	58	.32	8.0	0.063	1.6	5.00	MW	CG	N
0.975	24.77	72331S	1.75	44.5	.849	21.6	8.4	1.5	1.1	27	8.8	39	.32	8.0	0.063	1.6	5.00	SST	CG	N
0.975	24.77	72343	1.75	44.5	.831	21.1	15	2.6	1.2	32	18	82	.40	10.1	0.072	1.8	5.50	MW	CG	N
0.975	24.77	72343S	1.75	44.5	.831	21.1	13	2.2	.98	25	12	55	.40	10.1	0.072	1.8	5.50	SST	CG	N
0.975	24.77	72357	1.75	44.5	.827	21.0	16	2.7	1.3	33	20	89	.43	10.8	0.074	1.9	5.75	MW	CG	N
0.975	24.77	72357S	1.75	44.5	.827	21.0	13	2.3	1.0	26	13	60	.43	10.8	0.074	1.9	5.75	SST	CG	N
0.975	24.77	72371	1.75	44.5	.813	20.7	23	4.1	1.1	29	26	117	.47	11.8	0.081	2.1	5.75	MW	CG	N
0.975	24.77	72371S	1.75	44.5	.813	20.7	20	3.5	.89	23	18	78	.47	11.8	0.081	2.1	5.75	SST	CG	N
0.975	24.77	72383	1.75	44.5	.805	20.4	30	5.3	1.0	25	30	134	.47	11.9	0.085	2.2	5.50	MW	CG	N
0.975	24.77	72383S	1.75	44.5	.805	20.4	26	4.5	.79	20	20	90	.47	11.9	0.085	2.2	5.50	SST	CG	N
0.975	24.77	72384	1.75	44.5	.805	20.4	25	4.3	1.2	31	30	134	.53	13.5	0.085	2.2	6.25	MW	CG	N
0.975	24.77	72384S	1.75	44.5	.805	20.4	21	3.7	.96	24	20	90	.53	13.5	0.085	2.2	6.25	SST	CG	N
0.975	24.77	72407	1.75	44.5	.783	19.9	40	7.0	1.0	27	42	185	.62	15.8	0.096	2.4	6.50	MW	CG	N
0.975	24.77	72407S	1.75	44.5	.783	19.9	34	5.9	.82	21	28	123	.62	15.8	0.096	2.4	6.50	SST	CG	N
0.975	24.77	72419	1.75	44.5	.765	19.4	54	9.5	1.0	25	54	241	.72	18.3	0.105	2.7	6.88	MW	CG	N
0.975	24.77	72419S	1.75	44.5	.765	19.4	46	8.1	.78	20	36	160	.72	18.3	0.105	2.7	6.88	SST	CG	N
0.975	24.77	72432	1.75	44.5	.751	19.1	71	12	.89	23	63	281	.78	19.9	0.112	2.8	7.00	MW	CG	N
0.975	24.77	72432S	1.75	44.5	.751	19.1	60	11	.68	17	41	184	.78	19.9	0.112	2.8	7.00	SST	CG	N
0.975	24.77	72440	1.75	44.5	.745	18.9	78	14	.88	22	68	304	.82	20.8	0.115	2.9	7.13	MW	CG	N
0.975	24.77	72440S	1.75	44.5	.745	18.9	66	12	.67	17	45	199	.82	20.8	0.115	2.9	7.13	SST	CG	N
0.975	24.77	72448																		



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72441S	2.00	50.8	.745	18.9	58	10	.77	20	45	199	.91	23.0	0.115	2.9	7.88	SST	CG	N
0.975	24.77	72449	2.00	50.8	.735	18.7	82	14	.94	24	77	344	.95	24.0	0.120	3.0	7.88	MW	CG	N
0.975	24.77	72449S	2.00	50.8	.735	18.7	70	12	.73	18	51	225	.95	24.0	0.120	3.0	7.88	SST	CG	N
0.975	24.77	72460	2.00	50.8	.725	18.4	94	16	.93	24	87	388	1.02	25.8	0.125	3.2	8.13	MW	CG	N
0.975	24.77	72460S	2.00	50.8	.725	18.4	80	14	.71	18	57	253	1.02	25.8	0.125	3.2	8.13	SST	CG	N
0.975	24.77	72470	2.00	50.8	.705	17.9	126	22	.85	21	106	473	1.13	28.7	0.135	3.4	8.38	MW	CG	N
0.975	24.77	72470S	2.00	50.8	.705	17.9	107	19	.64	16	68	304	1.13	28.7	0.135	3.4	8.38	SST	CG	N
0.975	24.77	72477	2.00	50.8	.679	17.2	190	33	.73	19	139	617	1.24	31.5	0.148	3.8	8.38	MW	CG	N
0.975	24.77	72477S	2.00	50.8	.679	17.2	161	28	.55	14	89	397	1.24	31.5	0.148	3.8	8.38	SST	CG	N
0.975	24.77	72483	2.00	50.8	.651	16.5	291	51	.60	15	176	782	1.36	34.5	0.162	4.1	8.38	MW	CG	N
0.975	24.77	72483S	2.00	50.8	.651	16.5	248	43	.45	11	111	496	1.36	34.5	0.162	4.1	8.38	SST	CG	N
0.975	24.77	72333	2.25	57.2	.849	21.6	7.5	1.3	1.7	44	13	58	.38	9.6	0.063	1.6	6.00	MW	CG	N
0.975	24.77	72333S	2.25	57.2	.849	21.6	6.4	1.1	1.4	35	8.8	39	.38	9.6	0.063	1.6	6.00	SST	CG	N
0.975	24.77	72345	2.25	57.2	.831	21.1	11	2.0	1.6	41	18	82	.48	12.1	0.072	1.8	6.63	MW	CG	N
0.975	24.77	72345S	2.25	57.2	.831	21.1	9.7	1.7	1.3	33	12	55	.48	12.1	0.072	1.8	6.63	SST	CG	N
0.975	24.77	72360	2.25	57.2	.827	21.0	12	2.1	1.7	43	20	89	.52	13.2	0.074	1.9	7.00	MW	CG	N
0.975	24.77	72360S	2.25	57.2	.827	21.0	10	1.8	1.3	34	13	60	.52	13.2	0.074	1.9	7.00	SST	CG	N
0.975	24.77	72373	2.25	57.2	.813	20.7	18	3.1	1.5	38	26	117	.56	14.1	0.081	2.1	6.88	MW	CG	N
0.975	24.77	72373S	2.25	57.2	.813	20.7	15	2.6	1.2	30	18	78	.56	14.1	0.081	2.1	6.88	SST	CG	N
0.975	24.77	72386	2.25	57.2	.805	20.4	23	4.0	1.3	33	30	134	.56	14.3	0.085	2.2	6.63	MW	CG	N
0.975	24.77	72386S	2.25	57.2	.805	20.4	19	3.4	1.0	26	20	90	.56	14.3	0.085	2.2	6.63	SST	CG	N
0.975	24.77	72387	2.25	57.2	.805	20.4	19	3.3	1.6	41	30	134	.65	16.5	0.085	2.2	7.63	MW	CG	N
0.975	24.77	72387S	2.25	57.2	.805	20.4	16	2.8	1.3	32	20	90	.65	16.5	0.085	2.2	7.63	SST	CG	N
0.975	24.77	72409	2.25	57.2	.783	19.9	30	5.3	1.4	35	42	185	.77	19.5	0.096	2.4	8.00	MW	CG	N
0.975	24.77	72409S	2.25	57.2	.783	19.9	26	4.5	1.1	27	28	123	.77	19.5	0.096	2.4	8.00	SST	CG	N
0.975	24.77	72421	2.25	57.2	.765	19.4	41	7.2	1.3	33	54	241	.89	22.7	0.105	2.7	8.50	MW	CG	N
0.975	24.77	72421S	2.25	57.2	.765	19.4	35	6.1	1.0	26	36	160	.89	22.7	0.105	2.7	8.50	SST	CG	N
0.975	24.77	72434	2.25	57.2	.751	19.1	54	9.5	1.2	30	63	281	.95	24.2	0.112	2.8	8.50	MW	CG	N
0.975	24.77	72434S	2.25	57.2	.751	19.1	46	8.0	.90	23	41	184	.95	24.2	0.112	2.8	8.50	SST	CG	N
0.975	24.77	72442	2.25	57.2	.745	18.9	59	10	1.2	29	68	304	1.01	25.6	0.115	2.9	8.75	MW	CG	N
0.975	24.77	72442S	2.25	57.2	.745	18.9	50	8.8	.89	23	45	199	1.01	25.6	0.115	2.9	8.75	SST	CG	N
0.975	24.77	72450	2.25	57.2	.735	18.7	71	12	1.1	28	77	344	1.05	26.7	0.120	3.0	8.75	MW	CG	N
0.975	24.77	72450S	2.25	57.2	.735	18.7	60	11	.84	21	51	225	1.05	26.7	0.120	3.0	8.75	SST	CG	N
0.975	24.77	72461	2.25	57.2	.725	18.4	82	14	1.1	27	87	388	1.13	28.6	0.125	3.2	9.00	MW	CG	N
0.975	24.77	72461S	2.25	57.2	.725	18.4	70	12	.82	21	57	253	1.13	28.6	0.125	3.2	9.00	SST	CG	N
0.975	24.77	72334	2.50	63.5	.849	21.6	6.7	1.2	1.9	49	13	58	.40	10.2	0.063	1.6	6.38	MW	CG	N
0.975	24.77	72334S	2.50	63.5	.849	21.6	5.7	1.0	1.5	39	8.8	39	.40	10.2	0.063	1.6	6.38	SST	CG	N
0.975	24.77	72346	2.50	63.5	.831	21.1	10	1.8	1.8	46	18	82	.51	13.0	0.072	1.8	7.13	MW	CG	N
0.975	24.77	72346S	2.50	63.5	.831	21.1	8.6	1.5	1.4	36	12	55	.51	13.0	0.072	1.8	7.13	SST	CG	N
0.975	24.77	72361	2.50	63.5	.827	21.0	10	1.8	1.9	49	20	87	.57	14.6	0.074	1.9	7.75	MW	CG	N
0.975	24.77	72361S	2.50	63.5	.827	21.0	8.7	1.5	1.6	39	13	60	.57	14.6	0.074	1.9	7.75	SST	CG	N
0.975	24.77	72374	2.50	63.5	.813	20.7	16	2.8	1.7	42	26	117	.61	15.4	0.081	2.1	7.50	MW	CG	N
0.975	24.77	72374S	2.50	63.5	.813	20.7	13	2.4	1.3	33	18	78	.61	15.4	0.081	2.1	7.50	SST	CG	N
0.975	24.77	72388	2.50	63.5	.805	20.4	18	3.2	1.6	42	30	134	.66	16.7	0.085	2.2	7.75	MW	CG	N
0.975	24.77	72388S	2.50	63.5	.805	20.4	16	2.7	1.3	33	20	90	.66	16.7	0.085	2.2	7.75	SST	CG	N
0.975	24.77	72399	2.50	63.5	.791	20.1	22	3.8	1.7	42	36	160	.83	21.0	0.092	2.3	9.00	MW	CG	N
0.975	24.77	72399S	2.50	63.5	.791	20.1	18	3.2	1.3	34	24	108	.83	21.0	0.092	2.3	9.00	SST	CG	N
0.975	24.77	72410	2.50	63.5	.783	19.9	26	4.5	1.6	41	42	185	.85	21.6	0.096	2.4	8.88	MW	CG	N
0.975	24.77	72410S	2.50	63.5	.783	19.9	22	3.9	1.2	32	28	123	.85	21.6	0.096	2.4	8.88	SST	CG	N
0.975	24.77	72422	2.50	63.5	.765	19.4	36	6.4	1.5	38	54	241	.97	24.7	0.105	2.7	9.25	MW	CG	N
0.975	24.77	72422S	2.50	63.5	.765	19.4	31	5.4	1.2	29	36	160	.97	24.7	0.105	2.7	9.25	SST	CG	N
0.975	24.77	72435	2.50	63.5	.751	19.1	46	8.0	1.4	35	63	281	1.08	27.4	0.112	2.8	9.63	MW	CG	N
0.975	24.77	72435S	2.50	63.5	.751	19.1	39	6.8	1.1	27	41	184	1.08	27.4	0.112	2.8	9.63	SST	CG	N
0.975	24.77	72443	2.50	63.5	.745	18.9	52	9.1	1.3	33	68	304	1.11	28.1	0.115	2.9	9.63	MW	CG	N
0.975	24.77	72443S	2.50	63.5	.745	18.9	44	7.7	1.0	26	45	199	1.11	28.1	0.115	2.9	9.63	SST	CG	N
0.975	24.77	72451	2.50	63.5	.735	18.7	64	11	1.2	31	77	344	1.14	29.0	0.120	3.0	9.50	MW	CG	N
0.975	24.77	72451S	2.50	63.5																



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72423S	2.75	69.9	.765	19.4	28	4.9	1.3	33	36	160	1.06	27.0	0.105	2.7	10.1	SST	CG	N
0.975	24.77	72436	2.75	69.9	.751	19.1	43	7.5	1.5	37	63	281	1.13	28.8	0.112	2.8	10.1	MW	CG	N
0.975	24.77	72436S	2.75	69.9	.751	19.1	37	6.4	1.1	29	41	184	1.13	28.8	0.112	2.8	10.1	SST	CG	N
0.975	24.77	72463	2.75	69.9	.725	18.4	62	11	1.3	34	84	372	1.41	35.7	0.125	3.2	11.3	MW	CG	N
0.975	24.77	72463S	2.75	69.9	.725	18.4	53	9.3	1.1	27	57	253	1.41	35.7	0.125	3.2	11.3	SST	CG	N
0.975	24.77	72336	3.00	76.2	.849	21.6		5.6 .97	2.3	59	13	58	.46	11.8	0.063	1.6	7.38	MW	CG	N
0.975	24.77	72336S	3.00	76.2	.849	21.6		4.7 .83	1.9	47	8.8	39	.46	11.8	0.063	1.6	7.38	SST	CG	N
0.975	24.77	72348	3.00	76.2	.831	21.1		8.4 1.5	2.2	56	18	82	.59	15.1	0.072	1.8	8.25	MW	CG	N
0.975	24.77	72348S	3.00	76.2	.831	21.1		7.1 1.2	1.7	44	12	55	.59	15.1	0.072	1.8	8.25	SST	CG	N
0.975	24.77	72364	3.00	76.2	.827	21.0		8.4 1.5	2.3	59	20	87	.67	16.9	0.074	1.9	9.00	MW	CG	N
0.975	24.77	72364S	3.00	76.2	.827	21.0		7.1 1.3	1.9	48	13	60	.67	16.9	0.074	1.9	9.00	SST	CG	N
0.975	24.77	72376	3.00	76.2	.813	20.7	13	2.3	2.0	51	26	117	.70	17.7	0.081	2.1	8.63	MW	CG	N
0.975	24.77	72376S	3.00	76.2	.813	20.7	11	1.9	1.6	40	18	78	.70	17.7	0.081	2.1	8.63	SST	CG	N
0.975	24.77	72391	3.00	76.2	.805	20.4	15	2.6	2.0	51	30	134	.77	19.4	0.085	2.2	9.00	MW	CG	N
0.975	24.77	72391S	3.00	76.2	.805	20.4	13	2.3	1.6	40	20	90	.77	19.4	0.085	2.2	9.00	SST	CG	N
0.975	24.77	72400	3.00	76.2	.791	20.1	18	3.1	2.0	52	36	160	.97	24.5	0.092	2.3	10.5	MW	CG	N
0.975	24.77	72400S	3.00	76.2	.791	20.1	15	2.6	1.6	41	24	108	.97	24.5	0.092	2.3	10.5	SST	CG	N
0.975	24.77	72412	3.00	76.2	.783	19.9	21	3.7	1.9	49	42	185	1.00	25.3	0.096	2.4	10.4	MW	CG	N
0.975	24.77	72412S	3.00	76.2	.783	19.9	18	3.2	1.5	39	28	123	1.00	25.3	0.096	2.4	10.4	SST	CG	N
0.975	24.77	72424	3.00	76.2	.765	19.4	30	5.2	1.8	46	54	241	1.14	29.0	0.105	2.7	10.9	MW	CG	N
0.975	24.77	72424S	3.00	76.2	.765	19.4	25	4.4	1.4	36	36	160	1.14	29.0	0.105	2.7	10.9	SST	CG	N
0.975	24.77	72437	3.00	76.2	.751	19.1	38	6.6	1.7	43	63	281	1.26	32.0	0.112	2.8	11.3	MW	CG	N
0.975	24.77	72437S	3.00	76.2	.751	19.1	32	5.6	1.3	33	41	184	1.26	32.0	0.112	2.8	11.3	SST	CG	N
0.975	24.77	72444	3.00	76.2	.745	18.9	43	7.5	1.6	40	68	304	1.29	32.9	0.115	2.9	11.3	MW	CG	N
0.975	24.77	72444S	3.00	76.2	.745	18.9	37	6.4	1.2	31	45	199	1.29	32.9	0.115	2.9	11.3	SST	CG	N
0.975	24.77	72452	3.00	76.2	.735	18.7	52	9.1	1.5	38	77	344	1.34	33.9	0.120	3.0	11.1	MW	CG	N
0.975	24.77	72452S	3.00	76.2	.735	18.7	44	7.7	1.1	29	51	225	1.34	33.9	0.120	3.0	11.1	SST	CG	N
0.975	24.77	72464	3.00	76.2	.725	18.4	60	10	1.5	37	87	388	1.45	36.9	0.125	3.2	11.6	MW	CG	N
0.975	24.77	72464S	3.00	76.2	.725	18.4	51	8.9	1.1	29	57	253	1.45	36.9	0.125	3.2	11.6	SST	CG	N
0.975	24.77	72472	3.00	76.2	.705	17.9	80	14	1.3	34	106	473	1.64	41.6	0.135	3.4	12.1	MW	CG	N
0.975	24.77	72472S	3.00	76.2	.705	17.9	68	12	1.0	26	68	304	1.64	41.6	0.135	3.4	12.1	SST	CG	N
0.975	24.77	72479	3.00	76.2	.679	17.2	120	21	1.2	29	139	617	1.81	46.1	0.148	3.8	12.3	MW	CG	N
0.975	24.77	72479S	3.00	76.2	.679	17.2	102	18	.88	22	89	397	1.81	46.1	0.148	3.8	12.3	SST	CG	N
0.975	24.77	72485	3.00	76.2	.651	16.5	183	32	.96	24	176	782	1.96	49.9	0.162	4.1	12.1	MW	CG	N
0.975	24.77	72485S	3.00	76.2	.651	16.5	155	27	.72	18	111	496	1.96	49.9	0.162	4.1	12.1	SST	CG	N
0.975	24.77	72337	3.50	88.9	.849	21.6		4.7 .83	2.7	70	13	58	.52	13.2	0.063	1.6	8.25	MW	CG	N
0.975	24.77	72337S	3.50	88.9	.849	21.6		4.0 .71	2.2	56		8.8 39	.52	13.2	0.063	1.6	8.25	SST	CG	N
0.975	24.77	72349	3.50	88.9	.831	21.1		7.1 1.2	2.6	66	18	82	.68	17.1	0.072	1.8	9.38	MW	CG	N
0.975	24.77	72349S	3.50	88.9	.831	21.1		6.1 1.1	2.0	52	12	55	.68	17.1	0.072	1.8	9.38	SST	CG	N
0.975	24.77	72365	3.50	88.9	.827	21.0		7.1 1.2	2.7	70	19	87	.76	19.3	0.074	1.9	10.3	MW	CG	N
0.975	24.77	72365S	3.50	88.9	.827	21.0		6.0 1.1	2.2	57	13	60	.76	19.3	0.074	1.9	10.3	SST	CG	N
0.975	24.77	72377	3.50	88.9	.813	20.7	11	1.9	2.4	60	26	117	.79	20.1	0.081	2.1	9.75	MW	CG	N
0.975	24.77	72377S	3.50	88.9	.813	20.7		9.4 1.7	1.9	47	18	78	.79	20.1	0.081	2.1	9.75	SST	CG	N
0.975	24.77	72392	3.50	88.9	.805	20.4	13	2.3	2.3	60	30	134	.87	22.1	0.085	2.2	10.3	MW	CG	N
0.975	24.77	72392S	3.50	88.9	.805	20.4	11	1.9	1.9	47	20	90	.87	22.1	0.085	2.2	10.3	SST	CG	N
0.975	24.77	72401	3.50	88.9	.791	20.1	15	2.6	2.4	61	36	160	1.10	28.0	0.092	2.3	12.0	MW	CG	N
0.975	24.77	72401S	3.50	88.9	.791	20.1	13	2.2	1.9	48	24	108	1.10	28.0	0.092	2.3	12.0	SST	CG	N
0.975	24.77	72413	3.50	88.9	.783	19.9	18	3.2	2.3	58	42	185	1.14	29.0	0.096	2.4	11.9	MW	CG	N
0.975	24.77	72413S	3.50	88.9	.783	19.9	15	2.7	1.8	45	28	123	1.14	29.0	0.096	2.4	11.9	SST	CG	N
0.975	24.77	72425	3.50	88.9	.765	19.4	26	4.5	2.1	54	54	241	1.30	33.0	0.105	2.7	12.4	MW	CG	N
0.975	24.77	72425S	3.50	88.9	.765	19.4	22	3.8	1.6	42	36	160	1.30	33.0	0.105	2.7	12.4	SST	CG	N
0.975	24.77	72438	3.50	88.9	.751	19.1	32	5.6	2.0	50	63	281	1.46	37.0	0.112	2.8	13.0	MW	CG	N
0.975	24.77	72438S	3.50	88.9	.751	19.1	27	4.8	1.5	39	41	184	1.46	37.0	0.112	2.8	13.0	SST	CG	N
0.975	24.77	72445	3.50	88.9	.745	18.9	36	6.3	1.9	48	68	304	1.50	38.0	0.115	2.9	13.0	MW	CG	N
0.975	24.77	72445S	3.50	88.9	.745	18.9	31	5.4	1.5	37	45	199	1.50	38.0	0.115	2.9	13.0	SST	CG	N
0.975	24.77	72453	3.50	88.9	.735	18.7	44	7.7	1.8	45	77	344	1.55	39.2	0.120	3.0	12.9	MW	CG	N
0.975	24.77	72453S	3.50	88.9	.735	18.7	37	6.5	1.4	34	51	225	1.55	39.2	0.120					



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
0.975	24.77	72426S	4.00	101.6	.765	19.4	19	3.3	1.9	48	36	160	1.46	37.0	0.105	2.7	13.9	SST	CG	N
0.975	24.77	72439	4.00	101.6	.751	19.1	29	5.0	2.2	56	63	281	1.60	40.5	0.112	2.8	14.3	MW	CG	N
0.975	24.77	72439S	4.00	101.6	.751	19.1	24	4.3	1.7	43	41	184	1.60	40.5	0.112	2.8	14.3	SST	CG	N
0.975	24.77	72446	4.00	101.6	.745	18.9	32	5.6	2.1	54	68	304	1.65	42.0	0.115	2.9	14.4	MW	CG	N
0.975	24.77	72446S	4.00	101.6	.745	18.9	27	4.8	1.6	42	45	199	1.65	42.0	0.115	2.9	14.4	SST	CG	N
0.975	24.77	72454	4.00	101.6	.735	18.7	38	6.7	2.0	52	77	344	1.74	44.2	0.120	3.0	14.5	MW	CG	N
0.975	24.77	72454S	4.00	101.6	.735	18.7	32	5.7	1.6	40	51	225	1.74	44.2	0.120	3.0	14.5	SST	CG	N
0.975	24.77	72466	4.00	101.6	.725	18.4	44	7.7	2.0	51	87	388	1.89	48.0	0.125	3.2	15.1	MW	CG	N
0.975	24.77	72466S	4.00	101.6	.725	18.4	37	6.5	1.5	39	57	253	1.89	48.0	0.125	3.2	15.1	SST	CG	N
0.975	24.77	72474	4.00	101.6	.705	17.9	58	10	1.8	46	106	473	2.14	54.4	0.135	3.4	15.9	MW	CG	N
0.975	24.77	72474S	4.00	101.6	.705	17.9	50	8.7	1.4	35	68	304	2.14	54.4	0.135	3.4	15.9	SST	CG	N
0.975	24.77	72481	4.00	101.6	.679	17.2	87	15	1.6	40	139	617	2.37	60.1	0.148	3.8	16.0	MW	CG	N
0.975	24.77	72481S	4.00	101.6	.679	17.2	74	13	1.2	31	89	397	2.37	60.1	0.148	3.8	16.0	SST	CG	N
0.975	24.77	72487	4.00	101.6	.651	16.5	133	23	1.3	34	176	782	2.57	65.3	0.162	4.1	15.9	MW	CG	N
0.975	24.77	72487S	4.00	101.6	.651	16.5	113	20	.99	25	111	496	2.57	65.3	0.162	4.1	15.9	SST	CG	N
0.984	24.99	3336	.72	18.2	.794	20.2	111	19	.26	6.5	29	127	.33	8.4	0.095	2.4	3.50	SPR	CG	Z
0.984	24.99	2832	.81	20.6	.800	20.3	97	17	.38	9.5	36	162	.41	10.5	0.092	2.3	3.50	MW	C	Z
0.984	24.99	12579	.81	20.6	.794	20.2	111	19	.26	6.5	29	127	.33	8.5	0.095	2.4	3.50	SPR	CG	Z
0.984	24.99	S-3104	.88	22.2	.904	23.0	1.3	.22	.64	16	.81	3.6	.24	6.1	0.040	1.0	5.00	SST	C	N
0.984	24.99	10652	.94	23.8	.824	20.9	29	5.1	.48	12	14	62	.46	11.7	0.080	2.0	4.75	SPR	C	GI
0.984	24.99	1659	1.00	25.4	.860	21.8	11	1.9	.66	17	7.1	32	.34	8.7	0.062	1.6	4.50	SPR	C	Z
0.984	24.99	11942	1.00	25.4	.792	20.1	44	7.6	.42	11	18	82	.58	14.6	0.096	2.4	6.00	SPR	CG	Z
0.984	24.99	2635	1.00	25.4	.690	17.5	763	134	.18	4.5	135	600	.51	13.1	0.147	3.7	3.50	MW	CG	Z
0.984	24.99	3146	1.03	26.2	.894	22.7	2.5	.43	.81	21	2.0	8.9	.22	5.6	0.045	1.1	5.00	SPR	CG	Z
0.984	24.99	1513	1.06	27.0	.914	23.2	1.0	.18	.87	22	.88	3.9	.19	4.9	0.035	0.9	4.50	HD	C	Z
0.984	24.99	B12-24	1.06	27.0	.890	22.6	2.8	.50	.83	21	2.4	10	.24	6.0	0.047	1.2	5.00	SPR	CG	N
0.984	24.99	S-1048	1.19	30.2	.840	21.3	15	2.6	.83	21	12	54	.36	9.1	0.072	1.8	5.00	SST	CG	N
0.984	24.99	322	1.19	30.2	.824	20.9	30	5.2	.60	15	18	80	.45	11.5	0.080	2.0	4.67	SPR	C	GI
0.984	24.99	S-3087	1.25	31.8	.894	22.7	3.1	.54	1.0	26	3.2	14	.23	5.7	0.045	1.1	4.00	SST	C	N
0.984	24.99	3402	1.25	31.8	.656	16.7	539	94	.24	6.1	129	574	.90	22.9	0.164	4.2	5.50	SPR	CG	Z
0.984	24.99	11866	1.31	33.3	.862	21.9	13	2.2	.67	17	8.4	38	.31	7.7	0.061	1.5	4.00	SPR	C	N
0.984	24.99	12041	1.34	34.1	.674	17.1	485	85	.23	5.7	110	488	.78	19.7	0.155	3.9	5.00	SPR	CG	Z
0.984	24.99	S-183	1.41	35.7	.784	19.9	53	9.2	.58	15	31	137	.55	14.0	0.100	2.5	5.50	SST	CG	N
0.984	24.99	S-3084	1.47	37.3	.814	20.7	26	4.5	.78	20	20	89	.47	11.9	0.085	2.2	5.50	SST	CG	N
0.984	24.99	12205	1.50	38.1	.800	20.3	32	5.6	.81	20	26	116	.60	15.2	0.092	2.3	6.50	SPR	CG	Z
0.984	24.99	2599	1.50	38.1	.774	19.7	57	10	.67	17	38	171	.68	17.3	0.105	2.7	6.50	SPR	CG	Z
0.984	24.99	12704	1.63	41.3	.796	20.2	40	7.0	.97	25	38	171	.66	16.7	0.094	2.4	6.00	MW	C	N
0.984	24.99	S-1570	1.72	43.6	.916	23.3	.53	.09	1.5	38	.79	3.5	.23	5.8	0.034	0.9	5.75	SST	C	N
0.984	24.99	10861	1.75	44.5	.914	23.2	.60	.10	1.5	38	.90	4.0	.24	6.0	0.035	0.9	5.75	SST	C	N
0.984	24.99	II-78	1.75	44.5	.704	17.9	153	27	.55	14	84	372	1.12	28.4	0.140	3.6	8.00	SPR	CG	Z
0.984	24.99	S-470	1.78	45.2	.688	17.5	209	37	.42	11	89	394	1.04	26.3	0.148	3.8	7.00	SST	CG	N
0.984	24.99	S-1201	1.81	46.0	.814	20.7	9.0	1.6	.79	20	7.1	32	1.02	25.9	0.085	2.2	12.0	SST	CG	N
0.984	24.99	3862	1.88	47.6	.774	19.7	37	6.4	.93	24	34	152	.95	24.0	0.105	2.7	9.00	HD	CG	Z
0.984	24.99	B18-199	2.09	53.2	.784	19.9	31	5.4	1.0	25	31	137	.90	22.9	0.100	2.5	8.00	SST	C	N
0.984	24.99	12427	2.16	54.8	.884	22.5	3.3	.57	1.3	34	4.4	20	.30	7.6	0.050	1.3	5.00	SST	C	N
0.984	24.99	S-1590	2.25	57.2	.906	23.0	.58	.10	1.9	48	1.1	4.9	.35	8.9	0.039	1.0	8.00	SST	C	N
0.984	24.99	10395	2.25	57.2	.834	21.2	15	2.7	.98	25	15	66	.53	13.3	0.075	1.9	6.00	SPR	C	Z
0.984	24.99	11673	2.38	60.3	.686	17.4	187	33	.54	14	100	446	1.27	32.2	0.149	3.8	8.50	SPR	CG	Z
0.984	24.99	M-141	2.47	62.7	.484	12.3	2367	414	.16	4.1	385	1714	2.00	50.8	0.250	6.4	8.00	SPR	CG	Z
0.984	24.99	11752	2.50	63.5	.824	20.9	10	1.7	1.7	43	17	75	.80	20.3	0.080	2.0	10.0	SPR	CG	Z
0.984	24.99	2622	2.72	69.0	.600	15.2	562	98	.34	8.7	193	859	1.73	43.9	0.192	4.9	9.00	SPR	CG	Z
0.984	24.99	4371	3.00	76.2	.814	20.7	12	2.1	1.8	46	21	95	.91	23.2	0.085	2.2	10.8	SPR	CG	Z
0.984	24.99	1807	3.00	76.2	.774	19.7	22	3.9	1.6	40	35	157	1.42	36.0	0.105	2.7	13.5	HD	CG	Z
0.984	24.99	10429	3.50	88.9	.758	19.3	31	5.4	1.5	38	46	205	1.53	38.7	0.113	2.9	13.5	SPR	CG	Z
0.984	24.99	3188	3.63	92.1	.890	22.6	1.1	.19	3.1	79	3.3	15	.52	13.1	0.047	1.2	10.0	SPR	C	Z
0.984	24.99	10586	3.75	95.3	.820	20.8	6.0	1.1	2.5	64	15	68	1.23	31.2	0.082	2.1	15.0	SST	CG	N
0.984	24.99	11623	4.00	101.6	.626															



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.000	25.40	10164	1.25	31.8	.750	19.1	175	31	.35	8.9	61	271	.63	15.9	0.125	3.2	5.00	SPR	CG	Z
1.000	25.40	10251	1.25	31.8	.750	19.1	190	33	.32	8.1	61	271	.59	15.1	0.125	3.2	4.75	SPR	CG	Z
1.000	25.40	Q-82	1.34	34.1	.814	20.7	29	5.0	.69	18	20	89	.65	16.5	0.093	2.4	7.00	SPR	CG	N
1.000	25.40	S-899	1.38	34.9	.930	23.6		.52 .09	1.1	29	.59	2.6	.25	6.2	0.035	0.9	6.00	SST	C	N
1.000	25.40	00-90	1.38	34.9	.892	22.7	6.3	1.1	.87	22	5.4	24	.27	6.9	0.054	1.4	4.00	SST	CG	N
1.000	25.40	S-53	1.38	34.9	.840	21.3	17	3.0	.91	23	15	68	.47	11.9	0.080	2.0	6.00	SST	CG	N
1.000	25.40	S-1573	1.50	38.1	.892	22.7		3.7 .64	1.2	31	4.4	20	.30	7.5	0.054	1.4	5.50	SST	CG	N
1.000	25.40	2864	1.50	38.1	.790	20.1	54	9.5	.70	18	38	168	.68	17.3	0.105	2.7	6.50	HD	CG	Z
1.000	25.40	10969	1.50	38.1	.646	16.4	595	104	.27	6.8	158	704	1.11	28.2	0.177	4.5	6.25	HD	CG	BO
1.000	25.40	S-75	1.72	43.6	.790	20.1	41	7.2	.85	22	35	156	.76	19.3	0.105	2.7	7.25	SST	CG	N
1.000	25.40	10791	1.75	44.5	.930	23.6		.57 .10	1.5	38	.86	3.8	.24	6.0	0.035	0.9	5.75	SST	C	N
1.000	25.40	12523	1.75	44.5	.884	22.5	4.9	.85	1.4	36	6.8	30	.35	8.8	0.058	1.5	6.00	SPR	CG	Z
1.000	25.40	912	1.75	44.5	.876	22.3	5.7	1.0	1.3	33	7.3	33	.47	11.8	0.062	1.6	6.50	MW	C	Z
1.000	25.40	11812	1.75	44.5	.868	22.0	7.4	1.3	1.3	34	9.8	44	.43	10.9	0.066	1.7	6.50	SPR	CG	Z
1.000	25.40	11751	1.75	44.5	.840	21.3	22	3.8	.82	21	18	78	.44	11.2	0.080	2.0	5.50	SPR	CG	Z
1.000	25.40	11832	1.75	44.5	.790	20.1	41	7.2	.85	22	35	156	.76	19.3	0.105	2.7	7.25	SST	CG	N
1.000	25.40	3935	1.75	44.5	.760	19.3	87	15	.62	16	54	241	.84	21.3	0.120	3.0	7.00	SPR	CG	Z
1.000	25.40	S-3033	1.75	44.5	.704	17.9	194	34	.45	11	87	388	1.04	26.3	0.148	3.8	7.00	SST	CG	N
1.000	25.40	12260	1.78	45.2	.840	21.3	15	2.6	1.1	29	17	77	.64	16.3	0.080	2.0	7.00	SPR	C	Z
1.000	25.40	S-3195	1.88	47.6	.798	20.3	52	9.1	.60	15	31	139	.56	14.1	0.101	2.6	5.50	SST	CG	N
1.000	25.40	10561	1.94	49.2	.818	20.8	22	3.8	1.1	27	23	102	.67	16.9	0.091	2.3	7.33	SST	CG	N
1.000	25.40	S-1485	2.00	50.8	.918	23.3		1.3 .23	1.8	45	2.3	10	.25	6.2	0.041	1.0	5.00	SST	C	N
1.000	25.40	S-3021	2.00	50.8	.876	22.3		3.7 .65	1.5	38	5.6	25	.50	12.6	0.062	1.6	8.00	SST	CG	N
1.000	25.40	2767	2.00	50.8	.840	21.3	14	2.5	1.2	32	18	78	.59	14.9	0.080	2.0	7.33	HD	CG	Z
1.000	25.40	10091	2.00	50.8	.818	20.8	26	4.6	.94	24	25	110	.73	18.5	0.091	2.3	7.00	SPR	C	Z
1.000	25.40	1771	2.00	50.8	.760	19.3	109	19	.69	18	76	336	.84	21.3	0.120	3.0	6.00	MW	C	Z
1.000	25.40	10321	2.03	51.6	.774	19.7	75	13	.61	15	45	202	.73	18.7	0.113	2.9	6.50	SPR	CG	Z
1.000	25.40	10006	2.09	53.2	.676	17.2	240	42	.51	13	123	546	1.46	37.0	0.162	4.1	9.00	SPR	CG	Z
1.000	25.40	S-3226	2.13	54.0	.816	20.7	17	3.1	1.2	31	21	93	.92	23.4	0.092	2.3	9.00	SST	C	N
1.000	25.40	B17-189	2.13	54.0	.540	13.7	1469	257	.29	7.2	419	1862	1.84	46.7	0.230	5.8	8.00	MW	CG	Z
1.000	25.40	2662	2.16	54.8	.730	18.5	148	26	.50	13	74	330	.95	24.0	0.135	3.4	7.00	SPR	CG	Z
1.000	25.40	S-395	2.19	55.6	.898	22.8		3.3 .58	1.4	35	4.6	20	.31	7.8	0.051	1.3	5.00	SST	C	N
1.000	25.40	S-1386	2.19	55.6	.892	22.7		3.1 .55	1.7	44	5.4	24	.38	9.6	0.054	1.4	6.00	SST	C	N
1.000	25.40	S-3056	2.25	57.2	.910	23.1		1.2 .21	1.9	48	2.2	9.9	.36	9.1	0.045	1.1	7.00	SST	C	N
1.000	25.40	S-1147	2.25	57.2	.876	22.3		4.7 .83	1.7	44	8.2	36	.42	10.6	0.062	1.6	6.75	SST	CG	N
1.000	25.40	11391	2.25	57.2	.860	21.8		6.1 1.1	1.6	39	9.5	42	.70	17.8	0.070	1.8	9.00	SPR	C	Z
1.000	25.40	FF-79	2.25	57.2	.820	20.8	16	2.7	1.4	34	21	94	.90	22.9	0.090	2.3	10.0	SPR	CG	N
1.000	25.40	S-106	2.25	57.2	.706	17.9	171	30	.50	13	86	381	1.10	28.0	0.147	3.7	7.50	SST	CG	N
1.000	25.40	11912	2.28	57.9	.878	22.3		4.3 .75	1.8	47	7.8	35	.43	10.8	0.061	1.5	7.00	SST	CG	N
1.000	25.40	10697	2.31	58.7	.814	20.7	18	3.1	1.3	32	22	99	1.04	26.5	0.093	2.4	10.5	SPR	C	N
1.000	25.40	S-293	2.38	60.3	.790	20.1	30	5.3	1.2	29	35	156	.95	24.0	0.105	2.7	9.00	SST	CG	N
1.000	25.40	4141	2.38	60.3	.760	19.3	58	10	.93	24	54	241	1.26	32.0	0.120	3.0	9.50	SPR	C	Z
1.000	25.40	DD-67	2.50	63.5	.860	21.8		5.4 .94	1.8	46	9.7	43	.70	17.8	0.070	1.8	10.0	SPR	CG	Z
1.000	25.40	B17-184	2.50	63.5	.800	20.3	28	4.9	1.6	41	45	200	.90	22.9	0.100	2.5	9.00	MW	CG	GI
1.000	25.40	375	2.50	63.5	.790	20.1	35	6.1	1.1	28	38	168	1.05	26.7	0.105	2.7	9.00	HD	C	Z
1.000	25.40	71	2.50	63.5	.760	19.3	55	9.6	.99	25	54	241	1.20	30.5	0.120	3.0	10.0	HD	CG	Z
1.000	25.40	S-408	2.59	65.9	.676	17.2	260	45	.42	11	109	485	1.26	31.9	0.162	4.1	7.75	SST	CG	N
1.000	25.40	4311	2.63	66.7	.704	17.9	131	23	.74	19	97	431	1.55	39.5	0.148	3.8	10.5	SPR	CG	Z
1.000	25.40	10964	2.72	69.0	.750	19.1	62	11	.87	22	53	238	1.85	47.0	0.125	3.2	10.5	HD	CG	Z
1.000	25.40	2587	2.75	69.9	.866	22.0		5.9 1.0	1.8	47	11	49	.54	13.6	0.067	1.7	8.00	HD	CG	Z
1.000	25.40	12477	2.75	69.9	.840	21.3		9.5 1.7	1.9	47	18	78	.80	20.3	0.080	2.0	10.0	SPR	CG	Z
1.000	25.40	4207	2.88	73.0	.816	20.7	15	2.7	1.7	43	26	114	1.01	25.7	0.092	2.3	11.0	SPR	CG	Z
1.000	25.40	10358	2.94	74.6	.750	19.1	58	10	1.0	27	61	271	1.38	34.9	0.125	3.2	11.0	SPR	CG	Z
1.000	25.40	EE-56	3.00	76.2	.880	22.4		2.7 .46	2.4	60	6.3	28	.63	16.0	0.060	1.5	9.50	SST	C	N
1.000	25.40	10741	3.00	76.2	.876	22.3		2.0 .35	2.1	53	4.1	18	.93	23.6	0.062	1.6	15.0	SPR	CG	N
1.000	25.40	11135	3.00	76.2	.816	20.7	11	1.9	1.7	44	19	84	1.27	32.4	0.092	2.3	14.0	HD	CG	Z
1.000	25.40	3357	3.00	76.2	.782	19.9	29	5.0	1.5	37	42	188	1.31	33.2	0.109	2.8	12.0	SPR	CG	Z
1.000	25.40	57	3.00	76.2	.760	19.3	45	7.7												



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.000	25.40	7001	4.50	114.3	.760	19.3	25	4.4	2.1	53	53	234	2.40	61.0	0.120	3.0	19.5	HD	C	Z
1.000	25.40	656	4.50	114.3	.646	16.4	153	27	1.0	26	158	704	3.27	83.2	0.177	4.5	18.5	HD	CG	Z
1.000	25.40	1949	4.69	119.0	.704	17.9	74	13	1.3	33	97	431	2.52	63.9	0.148	3.8	17.0	SPR	CG	Z
1.000	25.40	4365	4.75	120.7	.840	21.3	6.0	1.1	2.9	74	18	78	1.16	29.5	0.080	2.0	14.5	SPR	CG	Z
1.000	25.40	3062	4.81	122.2	.818	20.8	12	2.1	2.1	52	25	110	1.17	29.8	0.091	2.3	13.0	SPR	CG	Z
1.000	25.40	10115	4.88	123.8	.676	17.2	120	21	1.0	26	123	546	2.59	65.8	0.162	4.1	16.0	SPR	CG	N
1.000	25.40	333	5.00	127.0	.646	16.4	137	24	1.2	29	158	704	3.63	92.2	0.177	4.5	20.5	HD	CG	Z
1.000	25.40	S-3106	5.13	130.2	.840	21.3	4.7	.82	3.5	89	17	73	1.28	32.5	0.080	2.0	16.0	SST	CG	N
1.000	25.40	S-270	5.13	130.2	.820	20.8	7.8	1.4	2.9	73	22	99	1.44	36.6	0.090	2.3	16.0	SST	CG	N
1.000	25.40	2605	5.25	133.4	.790	20.1	15	2.7	2.5	63	38	168	2.00	50.7	0.105	2.7	18.0	SPR	C	Z
1.000	25.40	12150	5.50	139.7	.700	17.8	54	9.4	1.8	46	98	437	3.60	91.4	0.150	3.8	24.0	SPR	CG	Z
1.000	25.40	848	6.00	152.4	.676	17.2	74	13	1.7	42	123	546	4.00	101.5	0.162	4.1	24.7	HD	CG	Z
1.000	25.40	11617	6.50	165.1	.814	20.7	8.0	1.4	3.3	84	26	118	1.95	49.6	0.093	2.4	20.0	SPR	CG	Z
1.000	25.40	2880	6.88	174.6	.706	17.9	49	8.6	1.9	49	95	423	3.53	89.6	0.147	3.7	24.0	SPR	CG	Z
1.000	25.40	S-1251	7.25	184.2	.818	20.8	8.2	1.4	2.8	72	23	102	1.46	37.0	0.091	2.3	16.0	SST	CG	N
1.000	25.40	12115	7.50	190.5	.660	16.8	66	11	1.7	44	113	502	5.78	146.8	0.170	4.3	34.0	SPR	CG	Z
1.000	25.40	S-121	8.00	203.2	.930	23.6	.15	.03	7.4	188	1.1	4.9	.60	15.1	0.035	0.9	16.0	SST	C	N
1.000	25.40	884	8.00	203.2	.818	20.8	5.6	.98	4.4	113	25	110	2.41	61.3	0.091	2.3	25.5	HD	C	Z
1.000	25.40	873	8.00	203.2	.790	20.1	9.3	1.6	4.1	103	38	168	2.97	75.3	0.105	2.7	28.3	HD	CG	Z
1.000	25.40	866	8.00	203.2	.760	19.3	15	2.7	3.5	90	54	241	3.78	96.0	0.120	3.0	30.5	HD	C	Z
1.000	25.40	856	8.00	203.2	.730	18.5	25	4.3	3.0	77	74	330	4.32	109.7	0.135	3.4	32.0	HD	CG	Z
1.000	25.40	S-464	8.00	203.2	.730	18.5	21	3.7	3.1	79	67	297	4.32	109.7	0.135	3.4	32.0	SST	CG	N
1.000	25.40	819	8.00	203.2	.704	17.9	37	6.4	2.7	67	97	431	4.81	122.2	0.148	3.8	32.5	HD	CG	Z
1.000	25.40	360	8.00	203.2	.586	14.9	183	32	1.3	33	235	1047	6.42	163.0	0.207	5.3	31.0	HD	CG	Z
1.000	25.40	10175	8.50	215.9	.646	16.4	114	20	1.4	35	158	704	4.29	109.0	0.177	4.5	24.3	SPR	CG	Z
1.000	25.40	2962	9.00	228.6	.790	20.1	8.3	1.5	4.5	115	38	168	3.39	86.0	0.105	2.7	31.3	SPR	C	Z
1.000	25.40	910	10.0	254.0	.790	20.1	7.0	1.2	5.4	138	38	168	3.99	101.3	0.105	2.7	37.0	HD	C	Z
1.000	25.40	11576	11.0	279.4	.828	21.0	3.5	.61	6.3	160	22	97	2.82	71.5	0.086	2.2	31.8	SPR	C	N
1.000	25.40	901	12.0	304.8	.856	21.7	1.8	.32	7.1	181	13	57	2.14	54.4	0.072	1.8	28.8	HD	C	Z
1.000	25.40	298	12.0	304.8	.840	21.3	2.4	.41	7.5	190	18	78	2.80	71.1	0.080	2.0	34.0	HD	C	Z
1.000	25.40	341	12.0	304.8	.616	15.6	99	17	1.9	49	190	847	7.58	192.6	0.192	4.9	39.5	HD	CG	Z
1.000	25.40	3069	16.8	425.5	.704	17.9	20	3.5	4.8	123	97	431	8.55	217.1	0.148	3.8	57.8	SPR	CG	GI
1.010	25.65	72489	1.00	25.4	.786	20.0	105	18	.44	11	46	206	.56	14.2	0.112	2.8	5.00	MW	CG	N
1.010	25.65	72489S	1.00	25.4	.786	20.0	90	16	.44	11	39	175	.56	14.2	0.112	2.8	5.00	SST	CG	N
1.010	25.65	72491	1.50	38.1	.786	20.0	64	11	.73	19	47	208	.77	19.6	0.112	2.8	6.88	MW	CG	N
1.010	25.65	72491S	1.50	38.1	.786	20.0	54	9.5	.73	19	40	177	.77	19.6	0.112	2.8	6.88	SST	CG	N
1.010	25.65	72493	2.00	50.8	.786	20.0	46	8.1	1.0	26	47	209	.98	24.9	0.112	2.8	8.75	MW	CG	N
1.010	25.65	72493S	2.00	50.8	.786	20.0	39	6.8	1.0	26	40	177	.98	24.9	0.112	2.8	8.75	SST	CG	N
1.010	25.65	72495	2.50	63.5	.786	20.0	36	6.3	1.3	33	47	207	1.20	30.6	0.112	2.8	10.8	MW	CG	N
1.010	25.65	72495S	2.50	63.5	.786	20.0	31	5.3	1.3	33	40	176	1.20	30.6	0.112	2.8	10.8	SST	CG	N
1.010	25.65	72497	3.00	76.2	.786	20.0	29	5.1	1.6	40	47	207	1.41	35.9	0.112	2.8	12.6	MW	CG	N
1.010	25.65	72497S	3.00	76.2	.786	20.0	25	4.4	1.6	40	40	176	1.41	35.9	0.112	2.8	12.6	SST	CG	N
1.010	25.65	72499	3.50	88.9	.786	20.0	25	4.4	1.9	48	47	208	1.62	41.2	0.112	2.8	14.5	MW	CG	N
1.010	25.65	72499S	3.50	88.9	.786	20.0	21	3.7	1.9	48	40	177	1.62	41.2	0.112	2.8	14.5	SST	CG	N
1.010	25.65	72501	4.00	101.6	.786	20.0	22	3.8	2.2	55	46	207	1.85	46.9	0.112	2.8	16.5	MW	CG	N
1.010	25.65	72501S	4.00	101.6	.786	20.0	18	3.2	2.2	55	40	176	1.85	46.9	0.112	2.8	16.5	SST	CG	N
1.010	25.65	72503	4.50	114.3	.786	20.0	19	3.3	2.4	62	47	207	2.06	52.3	0.112	2.8	18.4	MW	CG	N
1.010	25.65	72503S	4.50	114.3	.786	20.0	16	2.8	2.4	62	40	176	2.06	52.3	0.112	2.8	18.4	SST	CG	N
1.015	25.78	3882	.69	17.4	.775	19.7	416	73	.13	3.3	53	237	.36	9.1	0.120	3.0	3.00	HD	CG	Z
1.015	25.78	S-896	.88	22.2	.829	21.1	40	7.0	.41	10	16	73	.47	11.8	0.093	2.4	5.00	SST	CG	N
1.015	25.78	12136	1.28	32.5	.889	22.6	10	1.8	.86	22	9.0	40	.35	8.8	0.063	1.6	4.50	SPR	C	Z
1.015	25.78	S-1626	1.38	34.9	.909	23.1	5.7	.99	.90	23	5.1	23	.21	5.4	0.053	1.3	4.00	SST	CG	N
1.015	25.78	11694	1.50	38.1	.891	22.6	4.9	.86	1.1	27	5.2	23	.43	11.0	0.062	1.6	7.00	SPR	CG	Z
1.015	25.78	3390	1.50	38.1	.825	21.0	30	5.3	.84	21	25	112	.67	16.9	0.095	2.4	7.00	SPR	CG	Z
1.015	25.78	S-1021	1.63	41.3	.907	23.0	3.0	.52	1.3	33	3.9	17	.32	8.2	0.054	1.4	6.00	SST	CG	N
1.015	25.78	12059	1.69	42.8	.591	15.0	1869	327	.13	3.4	249	1106	1.06	26.9	0.212	5.4	5.0			



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.031	26.19	10107	.81	20.7	.907	23.0	12	2.0	.57	14	6.6	29	.25	6.3	0.062	1.6	4.00	SPR	CG	Z
1.031	26.19	S-3054	.88	22.2	.915	23.2	15	2.7	.43	11	6.5	29	.23	5.9	0.058	1.5	3.00	SST	C	N
1.031	26.19	A10-65	1.03	26.2	.869	22.1	21	3.7	.63	16	13	59	.41	10.3	0.081	2.1	5.00	SST	CG	N
1.031	26.19	2678	1.13	28.6	.849	21.6	40	6.9	.58	15	23	102	.55	13.9	0.091	2.3	5.00	HD	C	Z
1.031	26.19	10852	1.38	34.9	.875	22.2	18	3.2	.82	21	15	66	.39	9.9	0.078	2.0	5.00	SST	CG	N
1.031	26.19	3339	1.44	36.5	.907	23.0	4.9	.86	1.0	26	5.0	22	.42	10.6	0.062	1.6	6.75	HD	CG	GI
1.031	26.19	10740	1.50	38.1	.929	23.6	5.2	.90	.92	23	4.7	21	.20	5.2	0.051	1.3	4.00	SPR	CG	Z
1.031	26.19	S-1417	1.50	38.1	.857	21.8	17	3.0	.80	20	14	61	.70	17.7	0.087	2.2	7.00	SST	C	N
1.031	26.19	10659	1.53	38.9	.741	18.8	244	43	.36	9.3	89	395	.83	21.2	0.145	3.7	5.75	SPR	CG	Z
1.031	26.19	12447	1.56	39.7	.791	20.1	53	9.2	.42	11	22	99	1.14	29.0	0.120	3.0	9.50	SPR	CG	N
1.031	26.19	10409	1.94	49.2	.657	16.7	487	85	.35	9.0	172	766	1.50	38.0	0.187	4.7	8.00	SPR	CG	Z
1.031	26.19	10676	1.97	50.0	.807	20.5	36	6.4	.74	19	27	119	1.23	31.3	0.112	2.8	10.0	SPR	C	Z
1.031	26.19	S-1532	2.00	50.8	.923	23.4	2.8	.50	1.7	43	4.8	21	.32	8.2	0.054	1.4	6.00	SST	CG	N
1.031	26.19	10457	2.19	55.6	.707	18.0	224	39	.53	14	119	531	1.42	36.0	0.162	4.1	8.75	SPR	CG	Z
1.031	26.19	NN-20	2.19	55.6	.571	14.5	1305	228	.23	5.8	297	1321	1.84	46.7	0.230	5.8	8.00	SPR	CG	Z
1.031	26.19	10722	2.28	57.9	.747	19.0	145	25	.58	15	84	372	1.10	28.0	0.142	3.6	7.75	SPR	CG	Z
1.031	26.19	2730	2.34	59.5	.911	23.1	5.1	.89	1.9	49	9.8	44	.42	10.7	0.060	1.5	6.00	MW	C	Z
1.031	26.19	2702	2.47	62.7	.761	19.3	111	19	.91	23	101	449	1.08	27.4	0.135	3.4	8.00	MW	CG	Z
1.031	26.19	2677	2.63	66.7	.871	22.1	12	2.1	1.4	37	17	76	.62	15.7	0.080	2.0	7.75	HD	CG	Z
1.031	26.19	10988	2.81	71.4	.657	16.7	325	57	.53	13	172	766	2.06	52.2	0.187	4.7	11.0	HD	CG	Z
1.031	26.19	S-1473	3.00	76.2	.871	22.1	4.8	.83	1.8	47	8.8	39	1.16	29.5	0.080	2.0	14.5	SST	CG	N
1.031	26.19	3401	3.63	92.1	.917	23.3	1.5	.26	2.8	72	4.2	19	.80	20.3	0.057	1.4	13.0	SPR	C	Z
1.031	26.19	B18-197	3.75	95.3	.959	24.4	.49	.09	3.5	88	1.7	7.5	.29	7.3	0.036	0.9	7.00	SPR	C	Z
1.031	26.19	1631	3.75	95.3	.851	21.6	10	1.7	2.3	59	23	104	1.29	32.8	0.090	2.3	13.3	SPR	C	Z
1.031	26.19	B9-48	3.88	98.4	.637	16.2	325	57	.62	16	200	888	2.66	67.6	0.197	5.0	13.5	SPR	CG	N
1.031	26.19	12004	9.88	250.8	.837	21.3	4.9	.85	6.0	151	29	129	3.30	83.8	0.097	2.5	34.0	SPR	CG	Z
1.046	26.57	1895	.75	19.1	.944	24.0	9.9	1.7	.47	12	4.7	21	.20	5.2	0.051	1.3	3.00	HD	C	Z
1.046	26.57	S-1035	.81	20.6	.806	20.5	154	27	.31	7.8	47	211	.50	12.6	0.120	3.0	4.00	SST	CG	N
1.046	26.57	S-3004	.81	20.6	.806	20.5	163	29	.29	7.4	47	211	.48	12.2	0.120	3.0	4.00	SST	CG	N
1.046	26.57	10973	.94	23.8	.934	23.7	13	2.3	.45	11	5.8	26	.22	5.7	0.056	1.4	3.00	SST	C	N
1.046	26.57	B18-193	1.03	26.2	.866	22.0	36	6.3	.49	12	18	79	.54	13.7	0.090	2.3	5.00	SPR	C	Z
1.046	26.57	A14-56	1.19	30.2	.916	23.3	7.8	1.4	.83	21	6.4	29	.36	9.1	0.065	1.7	5.50	SPR	CG	Z
1.046	26.57	S-1444	1.31	33.3	.864	21.9	33	5.7	.67	17	22	98	.46	11.6	0.091	2.3	5.00	SST	CG	N
1.046	26.57	3338	1.44	36.5	.916	23.3	5.4	.95	.98	25	5.3	24	.46	11.6	0.065	1.7	7.00	SPR	CG	Z
1.046	26.57	2985	1.47	37.3	.806	20.5	94	16	.55	14	52	231	.72	18.3	0.120	3.0	6.00	SPR	CG	Z
1.046	26.57	S-1199	1.50	38.1	.930	23.6	2.9	.51	1.0	26	3.0	14	.46	11.8	0.058	1.5	7.00	SST	C	N
1.046	26.57	3826	1.50	38.1	.918	23.3	5.1	.89	1.1	27	5.4	24	.45	11.4	0.064	1.6	7.00	SPR	CG	Z
1.046	26.57	12066	1.50	38.1	.808	20.5	90	16	.56	14	51	225	.71	18.1	0.119	3.0	6.00	SPR	CG	Z
1.046	26.57	11561	1.69	42.8	.924	23.5	10	1.8	.76	19	8.0	35	.31	7.7	0.061	1.5	4.00	SPR	C	Z
1.046	26.57	12245	1.72	43.6	.884	22.5	14	2.4	1.2	29	16	71	.57	14.4	0.081	2.1	7.00	SPR	CG	GI
1.046	26.57	S-1496	1.81	46.0	.902	22.9	12	2.1	.96	24	12	52	.36	9.1	0.072	1.8	5.00	SST	CG	N
1.046	26.57	11231	1.91	48.4	.896	22.8	13	2.3	1.1	27	14	62	.51	12.9	0.075	1.9	5.75	SPR	C	Z
1.046	26.57	3213	2.00	50.8	.934	23.7	3.8	.66	1.6	42	6.2	27	.33	8.4	0.056	1.4	6.00	SPR	CG	Z
1.046	26.57	S-350	2.00	50.8	.836	21.2	52	9.1	.64	16	34	149	.58	14.7	0.105	2.7	5.50	SST	CG	N
1.046	26.57	3067	2.00	50.8	.750	19.1	159	28	.59	15	93	414	1.18	30.1	0.148	3.8	8.00	SPR	CG	Z
1.046	26.57	3757	2.25	57.2	.836	21.2	47	8.2	.78	20	36	161	.68	17.3	0.105	2.7	6.50	SPR	CG	Z
1.046	26.57	3009	2.25	57.2	.722	18.3	205	36	.58	15	118	525	1.46	37.0	0.162	4.1	9.00	SPR	CG	Z
1.046	26.57	S-1425	2.63	66.7	.896	22.8	6.9	1.2	1.9	48	13	58	.62	15.7	0.075	1.9	8.25	SST	C	N
1.046	26.57	S-3244	2.66	67.5	.898	22.8	6.6	1.2	1.9	49	13	56	.62	15.7	0.074	1.9	8.33	SST	CG	N
1.046	26.57	2744	3.88	98.4	.922	23.4	1.7	.29	2.9	73	4.8	21	1.01	25.6	0.062	1.6	15.3	HD	C	Z
1.046	26.57	11992	4.88	123.8	.822	20.9	21	3.7	2.0	50	42	189	1.68	42.7	0.112	2.8	15.0	SPR	CG	Z
1.046	26.57	3329	4.88	123.8	.722	18.3	96	17	1.2	31	118	525	2.75	70.0	0.162	4.1	17.0	SPR	CG	Z
1.046	26.57	11684	7.50	190.5	.790	20.1	28	4.8	2.3	58	63	279	2.88	73.2	0.128	3.3	22.0	SPR	CG	Z
1.046	26.57	3427	8.50	215.9	.846	21.5	8.9	1.6	3.5	89	31	140	2.10	53.3	0.100	2.5	21.0	SPR	CG	Z
1.062	26.97	AA-80	.88	22.2	.942	23.9	6.0	1.0	.59	15	3.5	16	.29	7.2	0.060	1.5	4.75	SST	CG	N
1.062	26.97	S-1394	.88	22.2	.938	23.8	7.4	1.3	.60	15	4.4	20	.28	7.1	0.062	1.6	4.50	SST	CG	N
1.062	26.97	S-311	.88	22.2	.914	23.2	26	4.5	.48	12	12	55	.26	6.6	0.074	1.9	3.50	SST	CG	N
1.062	26.97	4192	1.00	25.4	.938	23.8	11	1.9</												





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.062	26.97	11636	2.25	57.2	.842	21.4	35	6.1	1.1	29	40	176	.99	25.1	0.110	2.8	9.00	SPR	CG	Z
1.062	26.97	CC-44	2.25	57.2	.742	18.8	190	33	.53	13	100	443	1.28	32.5	0.160	4.1	8.00	SST	CG	N
1.062	26.97	12520	2.31	58.7	.812	20.6	71	12	.81	21	58	257	1.13	28.6	0.125	3.2	8.00	SPR	C	N
1.062	26.97	3133	2.38	60.3	.922	23.4	9.4	1.7	1.2	30	11	50	.47	12.0	0.070	1.8	5.75	SPR	C	Z
1.062	26.97	3942	2.50	63.5	.766	19.5	113	20	.81	21	92	408	1.48	37.6	0.148	3.8	10.0	SPR	CG	Z
1.062	26.97	A13-56	2.69	68.2	.916	23.3	4.4	.77	1.9	49	8.5	38	.77	19.5	0.073	1.9	10.5	SST	CG	N
1.062	26.97	S-437	3.38	85.7	.904	23.0	4.7	.83	2.4	60	11	49	1.02	25.8	0.079	2.0	13.0	SST	CG	N
1.062	26.97	S-1326	3.50	88.9	.918	23.3	3.5	.61	2.6	67	9.1	41	.86	21.9	0.072	1.8	12.0	SST	CG	N
1.062	26.97	3272	3.63	92.1	.848	21.5	22	3.8	1.7	44	38	168	1.28	32.6	0.107	2.7	12.0	SPR	CG	Z
1.062	26.97	12436	3.88	98.4	.938	23.8	2.2	.39	3.1	79	6.9	31	.78	19.7	0.062	1.6	11.5	SPR	C	Z
1.062	26.97	S-444	4.63	117.5	.862	21.9	12	2.0	2.5	62	29	128	1.40	35.6	0.100	2.5	14.0	SST	CG	N
1.062	26.97	S-3217	5.00	127.0	.992	25.2	.15	.03	4.5	114	.69	3.1	.51	12.9	0.035	0.9	13.5	SST	C	N
1.062	26.97	4108	5.00	127.0	.822	20.9	27	4.8	1.9	47	51	228	1.92	48.8	0.120	3.0	15.0	SPR	C	Z
1.062	26.97	334	6.00	152.4	.708	18.0	96	17	1.6	40	150	668	4.12	104.5	0.177	4.5	23.3	HD	CG	Z
1.062	26.97	2755	7.25	184.2	.738	18.7	61	11	1.9	49	116	518	3.94	100.1	0.162	4.1	24.3	SPR	CG	Z
1.062	26.97	1936	7.63	193.7	.880	22.4	6.3	1.1	3.7	94	23	104	1.73	43.9	0.091	2.3	19.0	SPR	CG	Z
1.062	26.97	1703	7.63	193.7	.738	18.7	60	10	1.9	49	116	518	4.16	105.6	0.162	4.1	24.7	SPR	C	Z
1.062	26.97	385	11.5	292.1	.852	21.6	12	2.2	2.9	73	36	159	2.00	50.7	0.105	2.7	18.0	HD	C	Z
1.062	26.97	4170	11.5	292.1	.852	21.6	5.7	1.0	6.3	159	36	159	3.99	101.3	0.105	2.7	37.0	SPR	C	Z
1.070	27.18	12804	4.00	101.6	.656	16.7	315	55	.71	18	223	991	3.10	78.7	0.207	5.3	15.0	HD	CG	Z
1.078	27.38	11507	.78	19.8	.934	23.7	19	3.3	.42	11	8.0	36	.36	9.1	0.072	1.8	4.00	SPR	CG	Z
1.078	27.38	12074	1.00	25.4	.918	23.3	30	5.2	.55	14	16	73	.32	8.1	0.080	2.0	4.00	SPR	CG	Z
1.078	27.38	10525	1.00	25.4	.868	22.0	47	8.3	.37	9.4	18	78	.63	16.0	0.105	2.7	6.00	SPR	CG	Z
1.078	27.38	11702	1.13	28.6	.992	25.2	1.3	.22	.89	23	1.1	5.0	.24	6.0	0.043	1.1	5.50	SPR	CG	Z
1.078	27.38	10685	1.13	28.6	.908	23.1	27	4.8	.66	17	18	79	.47	11.9	0.085	2.2	4.50	SST	C	N
1.078	27.38	11728	1.13	28.6	.828	21.0	135	24	.42	11	57	253	.63	15.9	0.125	3.2	5.00	SPR	CG	Z
1.078	27.38	12318	1.19	30.2	.992	25.2	1.3	.22	.91	23	1.2	5.1	.28	7.1	0.043	1.1	5.50	SPR	C	Z
1.078	27.38	11850	1.34	34.1	.922	23.4	12	2.1	.88	22	10	46	.47	11.9	0.078	2.0	6.00	SST	CG	N
1.078	27.38	12307	1.47	37.3	.958	24.3	3.5	.62	.99	25	3.5	16	.48	12.2	0.060	1.5	7.00	SPR	C	Z
1.078	27.38	A13-69	1.47	37.3	.894	22.7	23	4.0	.90	23	21	93	.56	14.3	0.092	2.3	6.13	SST	CG	N
1.078	27.38	12268	1.50	38.1	.966	24.5	3.8	.66	1.2	30	4.5	20	.31	7.8	0.056	1.4	5.50	SPR	CG	Z
1.078	27.38	1908	1.50	38.1	.852	21.6	65	11	.65	16	42	188	.68	17.2	0.113	2.9	6.00	SPR	CG	Z
1.078	27.38	1739	1.63	41.3	.782	19.9	229	40	.55	14	127	564	.85	21.6	0.148	3.8	5.75	MW	CG	Z
1.078	27.38	1741	1.75	44.5	.896	22.8	34	6.0	.68	17	23	103	.55	13.9	0.091	2.3	5.00	HD	C	Z
1.078	27.38	11564	1.81	46.0	.960	24.4	4.7	.82	1.4	36	6.7	30	.38	9.7	0.059	1.5	5.50	SPR	CG	Z
1.078	27.38	S-844	1.88	47.6	.908	23.1	14	2.4	1.3	33	18	78	.58	14.8	0.085	2.2	6.88	SST	CG	N
1.078	27.38	S-356	2.00	50.8	.988	25.1	1.6	.27	1.7	44	2.7	12	.27	6.9	0.045	1.1	5.00	SST	C	N
1.078	27.38	11586	2.00	50.8	.896	22.8	21	3.6	1.1	29	23	103	.73	18.5	0.091	2.3	7.00	SPR	CG	N
1.078	27.38	12156	2.00	50.8	.808	20.5	104	18	.67	17	69	308	1.01	25.7	0.135	3.4	7.50	SPR	CG	Z
1.078	27.38	B11-29	2.00	50.8	.808	20.5	127	22	.55	14	69	308	.88	22.3	0.135	3.4	6.50	SPR	CG	N
1.078	27.38	10992	2.00	50.8	.754	19.2	224	39	.51	13	115	511	1.42	36.0	0.162	4.1	7.75	HD	CG	Z
1.078	27.38	10939	2.06	52.4	.934	23.7	6.3	1.1	1.5	38	9.4	42	.58	14.6	0.072	1.8	8.00	SPR	CG	Z
1.078	27.38	3121	2.13	54.0	.934	23.7	9.5	1.7	1.3	32	12	53	.43	11.0	0.072	1.8	6.00	SPR	CG	Z
1.078	27.38	11870	2.13	54.0	.894	22.7	20	3.4	1.2	31	24	106	.69	17.5	0.092	2.3	7.50	SPR	CG	N
1.078	27.38	11165	2.13	54.0	.782	19.9	202	35	.45	11	91	403	.93	23.5	0.148	3.8	6.25	SPR	CG	Z
1.078	27.38	S-129	2.19	55.6	.932	23.7	8.2	1.4	1.4	36	12	52	.46	11.6	0.073	1.9	6.25	SST	CG	N
1.078	27.38	S-3166	2.25	57.2	.954	24.2	4.1	.73	1.8	47	7.6	34	.39	9.8	0.062	1.6	6.25	SST	CG	N
1.078	27.38	S-1672	2.25	57.2	.898	22.8	14	2.5	1.4	36	21	92	.72	18.3	0.090	2.3	8.00	SST	CG	N
1.078	27.38	B17-132	2.50	63.5	1.026	26.1	.08	.01	2.3	58	.19	.84	.23	5.9	0.026	0.7	8.00	SST	C	N
1.078	27.38	S-422	2.50	63.5	.894	22.7	18	3.1	1.2	32	22	98	.67	16.9	0.092	2.3	7.25	SST	CG	N
1.078	27.38	11827	2.50	63.5	.808	20.5	70	12	.90	23	62	277	1.25	31.7	0.135	3.4	9.25	SST	CG	N
1.078	27.38	10369	2.50	63.5	.796	20.2	138	24	.57	14	79	350	.99	25.1	0.141	3.6	7.00	SPR	CG	Z
1.078	27.38	2649	2.50	63.5	.784	19.9	104	18	.85	22	89	395	1.47	37.3	0.147	3.7	10.0	HD	CG	Z
1.078	27.38	RR-58	2.75	69.9	.998	25.3	.41	.07	2.3	59	.95	4.2	.44	11.2	0.040	1.0	10.0	SPR	C	Z
1.078	27.38	11759	2.84	72.2	.954	24.2	1.6	.27	1.9	47	2.9	13	.99	25.2	0.062	1.6	15.0	SPR	C	Z
1.078	27.38	S-95	3.00	76.2	.578	14.7	1075	188	.28	7.2	304	1352	2.50	63.5	0.250	6.4	10.0	SST	CG	N
1.078	27.38	2698	3.75	95.3	.748	19.0	1													




1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.094	27.79	12111	1.53	38.9	.934	23.7	11	1.9	.93	24	10	46	.60	15.2	0.080	2.0	6.50	SST	C	N
1.094	27.79	3132	1.59	40.5	.894	22.7	33	5.7	.92	23	30	134	.65	16.5	0.100	2.5	6.50	SPR	CG	Z
1.094	27.79	12006	1.59	40.5	.782	19.9	295	52	.34	8.8	102	452	.86	21.8	0.156	4.0	5.50	SPR	CG	Z
1.094	27.79	1671	1.63	41.3	.798	20.3	217	38	.41	10	89	397	.85	21.6	0.148	3.8	5.75	SPR	CG	Z
1.094	27.79	11278	1.69	42.8	.782	19.9	258	45	.39	10	102	452	.94	23.8	0.156	4.0	6.00	SPR	CG	Z
1.094	27.79	10332	1.88	47.6	.810	20.6	159	28	.50	13	79	352	.89	22.6	0.142	3.6	6.25	SPR	CG	Z
1.094	27.79	945	2.00	50.8	.974	24.7	3.7	.66	1.6	39	5.8	26	.45	11.4	0.060	1.5	6.50	MW	C	Z
1.094	27.79	1577	2.00	50.8	.884	22.5	34	5.9	1.0	26	35	154	.77	19.6	0.105	2.7	7.33	SPR	CG	Z
1.094	27.79	3262	2.00	50.8	.824	20.9	98	17	.69	18	68	304	1.01	25.7	0.135	3.4	7.50	HD	CG	Z
1.094	27.79	10325	2.13	54.0	.810	20.6	135	24	.58	15	79	352	.99	25.2	0.142	3.6	7.00	SPR	CG	Z
1.094	27.79	S-1246	2.19	55.6	.950	24.1	7.9	1.4	1.4	36	11	49	.43	11.0	0.072	1.8	6.00	SST	C	N
1.094	27.79	11284	2.19	55.6	.798	20.3	172	30	.52	13	89	397	1.00	25.4	0.148	3.8	6.75	SPR	CG	Z
1.094	27.79	3697	2.25	57.2	1.006	25.6	1.2	.20	1.9	49	2.3	10	.31	7.8	0.044	1.1	6.00	SPR	C	Z
1.094	27.79	11971	2.38	60.3	.914	23.2	14	2.5	1.4	36	20	91	.70	17.7	0.090	2.3	7.75	SST	CG	N
1.094	27.79	11381	2.50	63.5	.944	24.0	7.6	1.3	1.6	42	13	56	.53	13.3	0.075	1.9	7.00	SST	CG	N
1.094	27.79	3309	2.50	63.5	.814	20.7	91	16	.84	21	76	338	1.26	32.0	0.140	3.6	9.00	SPR	CG	Z
1.094	27.79	S-448	2.63	66.7	.872	22.1	32	5.6	1.1	29	36	161	.92	23.3	0.111	2.8	8.25	SST	CG	N
1.094	27.79	10381	2.63	66.7	.868	22.0	31	5.4	1.3	34	42	186	1.13	28.7	0.113	2.9	10.0	SPR	CG	Z
1.094	27.79	3913	2.75	69.9	1.012	25.7	.43	.08	2.3	58	1.0	4.4	.45	11.5	0.041	1.0	10.0	SPR	C	Z
1.094	27.79	S-1439	2.75	69.9	.992	25.2	1.4	.24	2.3	59	3.1	14	.43	11.0	0.051	1.3	7.50	SST	C	N
1.094	27.79	3163	2.75	69.9	.782	19.9	163	29	.62	16	102	452	1.33	33.9	0.156	4.0	8.50	SPR	CG	Z
1.094	27.79	11388	3.41	86.5	.844	21.4	38	6.7	1.3	34	51	228	1.38	34.9	0.125	3.2	11.0	SST	CG	N
1.094	27.79	S-279	3.63	92.1	.912	23.2	6.3	1.1	2.2	56	14	62	1.41	35.8	0.091	2.3	15.5	SST	CG	N
1.094	27.79	3711	4.00	101.6	.984	25.0	1.2	.21	3.3	83	3.9	17	.72	18.2	0.055	1.4	12.0	SPR	C	Z
1.094	27.79	3374	4.00	101.6	.814	20.7	55	9.7	1.4	35	76	338	1.89	48.0	0.140	3.6	13.5	SPR	CG	GI
1.094	27.79	12169	4.06	103.2	.782	19.86	115	20	.88	22.35	101	447	1.72	43.69	0.158	4.0	11.0	SPR	CG	GI
1.094	27.79	10948	4.19	106.4	.854	21.7	26	4.6	1.7	44	45	202	1.56	39.6	0.120	3.0	13.0	SST	CG	N
1.094	27.79	2713	4.75	120.7	.894	22.7	11	1.9	2.8	70	30	134	1.55	39.4	0.100	2.5	15.5	SPR	CG	Z
1.094	27.79	11775	4.91	124.6	.900	22.9	9.7	1.7	2.6	67	25	113	1.33	33.9	0.097	2.5	13.8	SST	CG	N
1.094	27.79	12312	5.00	127.0	.884	22.5	15	2.6	2.3	59	35	154	1.58	40.0	0.105	2.7	14.0	HD	C	Z
1.094	27.79	S-3046	5.13	130.2	.844	21.4	24	4.2	2.1	54	51	228	2.00	50.8	0.125	3.2	16.0	SST	CG	N
1.094	27.79	4130	5.38	136.5	.914	23.2	9.3	1.6	2.4	60	22	98	1.08	27.4	0.090	2.3	12.0	SPR	CG	Z
1.094	27.79	11709	6.00	152.4	.910	23.1	7.9	1.4	3.0	76	24	105	1.38	35.1	0.092	2.3	15.0	SPR	CG	Z
1.094	27.79	3471	7.50	190.5	.766	19.5	57	10	2.0	52	117	522	4.18	106.2	0.164	4.2	24.5	SPR	C	Z
1.094	27.79	1643	7.88	200.0	.884	22.5	7.5	1.3	4.6	117	35	154	2.73	69.3	0.105	2.7	26.0	SPR	CG	Z
1.094	27.79	12180	8.19	207.9	.888	22.6	6.9	1.2	4.7	120	33	146	2.68	68.0	0.103	2.6	26.0	SPR	CG	Z
1.094	27.79	361	11.3	285.8	.740	18.8	46	8.0	3.2	81	146	651	7.43	188.8	0.177	4.5	42.0	HD	CG	Z
1.100	27.94	72504	.88	22.4	.936	23.8	43	7.5	.57	14	24	108	.29	7.3	0.082	2.1	3.50	MW	CG	N
1.100	27.94	72504S	.88	22.4	.936	23.8	36	6.3	.45	11	16	72	.29	7.3	0.082	2.1	3.50	SST	CG	N
1.100	27.94	72514	.88	22.4	.930	23.6	45	7.9	.57	15	26	115	.31	7.8	0.085	2.2	3.63	MW	CG	N
1.100	27.94	72514S	.88	22.4	.930	23.6	38	6.7	.47	12	18	80	.31	7.8	0.085	2.2	3.63	SST	CG	N
1.100	27.94	72527	.88	22.4	.914	23.2	65	11	.52	13	34	150	.34	8.6	0.093	2.4	3.63	MW	CG	N
1.100	27.94	72527S	.88	22.4	.914	23.2	55	9.6	.41	10	22	100	.34	8.6	0.093	2.4	3.63	SST	CG	N
1.100	27.94	72537	.88	22.4	.908	23.1	70	12	.52	13	36	161	.36	9.1	0.096	2.4	3.75	MW	CG	N
1.100	27.94	72537S	.88	22.4	.908	23.1	59	10	.41	11	25	109	.36	9.1	0.096	2.4	3.75	SST	CG	N
1.100	27.94	72549	.88	22.4	.890	22.6	98	17	.47	12	46	206	.41	10.3	0.105	2.7	3.88	MW	CG	N
1.100	27.94	72549S	.88	22.4	.890	22.6	83	15	.39	9.8	32	142	.41	10.3	0.105	2.7	3.88	SST	CG	N
1.100	27.94	72560	.88	22.4	.876	22.3	126	22	.45	11	56	249	.43	11.0	0.112	2.8	3.88	MW	CG	N
1.100	27.94	72560S	.88	22.4	.876	22.3	107	19	.35	8.8	37	164	.43	11.0	0.112	2.8	3.88	SST	CG	N
1.100	27.94	72582	.88	22.4	.850	21.6	194	34	.38	9.7	74	328	.50	12.7	0.125	3.2	4.00	MW	CG	N
1.100	27.94	72582S	.88	22.4	.850	21.6	165	29	.31	7.8	51	227	.50	12.7	0.125	3.2	4.00	SST	CG	N
1.100	27.94	72505	1.00	25.4	.936	23.8	36	6.3	.67	17	24	108	.31	7.8	0.082	2.1	3.75	MW	CG	N
1.100	27.94	72505S	1.00	25.4	.936	23.8	31	5.4	.53	13	16	72	.31	7.8	0.082	2.1	3.75	SST	CG	N
1.100	27.94	72515	1.00	25.4	.930	23.6	38	6.7	.67	17	26	114	.33	8.4	0.085	2.2	3.88	MW	CG	N
1.100	27.94	72515S	1.00	25.4	.930	23.6	33	5.7	.55	14	18	80	.33	8.4	0.085	2.2	3.88	SST	CG	N
1.100	27.94	72528	1.00	25.4	.914	23.2	55	9.6	.62	16	34	150	.36	9.2	0.093	2.4	3.88	MW	CG	N
1.100	27.94	72528S	1.00	25.4	.914	23.2	46	8.1	.48	12	22	100	.36	9.2	0.093	2.4	3.88	SST	CG	N
1.100	27.94	72538	1.00	25.4	.9															



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.100	27.94	72584S	1.25	31.8	.850	21.6	104	18	.49	12	51	227	.64	16.3	0.125	3.2	5.13	SST	CG	N
1.100	27.94	72507	1.50	38.1	.936	23.8	23	4.0	1.1	27	24	108	.39	9.9	0.082	2.1	4.75	MW	CG	N
1.100	27.94	72507S	1.50	38.1	.936	23.8	19	3.4	.84	21	16	72	.39	9.9	0.082	2.1	4.75	SST	CG	N
1.100	27.94	72517	1.50	38.1	.930	23.6	24	4.2	1.1	27	26	114	.43	10.8	0.085	2.2	5.00	MW	CG	N
1.100	27.94	72517S	1.50	38.1	.930	23.6	20	3.6	.89	23	18	80	.43	10.8	0.085	2.2	5.00	SST	CG	N
1.100	27.94	72530	1.50	38.1	.914	23.2	34	6.0	.98	25	34	150	.48	12.1	0.093	2.4	5.13	MW	CG	N
1.100	27.94	72530S	1.50	38.1	.914	23.2	29	5.1	.77	19	22	100	.48	12.1	0.093	2.4	5.13	SST	CG	N
1.100	27.94	72540	1.50	38.1	.908	23.1	37	6.4	1.0	25	36	162	.50	12.8	0.096	2.4	5.25	MW	CG	N
1.100	27.94	72540S	1.50	38.1	.908	23.1	31	5.4	.79	20	25	109	.50	12.8	0.096	2.4	5.25	SST	CG	N
1.100	27.94	72552	1.50	38.1	.890	22.6	50	8.8	.92	23	46	206	.58	14.7	0.105	2.7	5.50	MW	CG	N
1.100	27.94	72552S	1.50	38.1	.890	22.6	43	7.5	.75	19	32	142	.58	14.7	0.105	2.7	5.50	SST	CG	N
1.100	27.94	72563	1.50	38.1	.876	22.3	68	12	.84	21	56	251	.62	15.6	0.112	2.8	5.50	MW	CG	N
1.100	27.94	72563S	1.50	38.1	.876	22.3	57	10	.64	16	37	164	.62	15.6	0.112	2.8	5.50	SST	CG	N
1.100	27.94	72573	1.50	38.1	.860	21.8	93	16	.75	19	69	308	.65	16.4	0.120	3.0	5.38	MW	CG	N
1.100	27.94	72573S	1.50	38.1	.860	21.8	79	14	.57	15	45	201	.65	16.4	0.120	3.0	5.38	SST	CG	N
1.100	27.94	72585	1.50	38.1	.850	21.6	105	18	.74	19	78	347	.70	17.9	0.125	3.2	5.63	MW	CG	N
1.100	27.94	72585S	1.50	38.1	.850	21.6	89	16	.57	15	51	227	.70	17.9	0.125	3.2	5.63	SST	CG	N
1.100	27.94	72594	1.50	38.1	.830	21.1	137	24	.69	18	95	423	.79	20.1	0.135	3.4	5.88	MW	CG	N
1.100	27.94	72594S	1.50	38.1	.830	21.1	116	20	.53	13	61	272	.79	20.1	0.135	3.4	5.88	SST	CG	N
1.100	27.94	72508	1.75	44.5	.936	23.8	19	3.3	1.3	32	24	108	.43	10.9	0.082	2.1	5.25	MW	CG	N
1.100	27.94	72508S	1.75	44.5	.936	23.8	16	2.8	1.0	25	16	72	.43	10.9	0.082	2.1	5.25	SST	CG	N
1.100	27.94	72519	1.75	44.5	.930	23.6	21	3.6	1.3	33	27	119	.47	11.9	0.085	2.2	5.50	MW	CG	N
1.100	27.94	72519S	1.75	44.5	.930	23.6	18	3.1	1.0	26	18	80	.47	11.9	0.085	2.2	5.50	SST	CG	N
1.100	27.94	72531	1.75	44.5	.914	23.2	29	5.1	1.2	30	34	150	.52	13.3	0.093	2.4	5.63	MW	CG	N
1.100	27.94	72531S	1.75	44.5	.914	23.2	25	4.3	.91	23	22	100	.52	13.3	0.093	2.4	5.63	SST	CG	N
1.100	27.94	72542	1.75	44.5	.908	23.1	31	5.3	1.2	30	36	159	.58	14.6	0.096	2.4	6.00	MW	CG	N
1.100	27.94	72542S	1.75	44.5	.908	23.1	26	4.5	.95	24	25	109	.58	14.6	0.096	2.4	6.00	SST	CG	N
1.100	27.94	72553	1.75	44.5	.890	22.6	42	7.4	1.1	28	46	204	.66	16.7	0.105	2.7	6.25	MW	CG	N
1.100	27.94	72553S	1.75	44.5	.890	22.6	36	6.3	.90	23	32	142	.66	16.7	0.105	2.7	6.25	SST	CG	N
1.100	27.94	72564	1.75	44.5	.876	22.3	56	9.9	1.0	25	56	251	.69	17.4	0.112	2.8	6.13	MW	CG	N
1.100	27.94	72564S	1.75	44.5	.876	22.3	48	8.4	.77	20	37	164	.69	17.4	0.112	2.8	6.13	SST	CG	N
1.100	27.94	72574	1.75	44.5	.860	21.8	77	14	.90	23	69	308	.74	18.7	0.120	3.0	6.13	MW	CG	N
1.100	27.94	72574S	1.75	44.5	.860	21.8	66	11	.69	17	45	201	.74	18.7	0.120	3.0	6.13	SST	CG	N
1.100	27.94	72586	1.75	44.5	.850	21.6	86	15	.90	23	78	347	.80	20.2	0.125	3.2	6.38	MW	CG	N
1.100	27.94	72586S	1.75	44.5	.850	21.6	73	13	.69	18	51	227	.80	20.2	0.125	3.2	6.38	SST	CG	N
1.100	27.94	72596	1.75	44.5	.830	21.1	113	20	.84	21	95	423	.89	22.7	0.135	3.4	6.63	MW	CG	N
1.100	27.94	72596S	1.75	44.5	.830	21.1	96	17	.63	16	61	272	.89	22.7	0.135	3.4	6.63	SST	CG	N
1.100	27.94	72605	1.75	44.5	.816	20.7	150	26	.73	19	110	490	.91	23.0	0.142	3.6	6.38	MW	CG	N
1.100	27.94	72605S	1.75	44.5	.816	20.7	128	22	.56	14	71	316	.91	23.0	0.142	3.6	6.38	SST	CG	N
1.100	27.94	72617	1.75	44.5	.804	20.4	175	31	.71	18	124	553	.98	24.9	0.148	3.8	6.63	MW	CG	N
1.100	27.94	72617S	1.75	44.5	.804	20.4	149	26	.54	14	80	356	.98	24.9	0.148	3.8	6.63	SST	CG	N
1.100	27.94	72509	2.00	50.8	.936	23.8	17	2.9	1.5	37	24	108	.47	12.0	0.082	2.1	5.75	MW	CG	N
1.100	27.94	72509S	2.00	50.8	.936	23.8	14	2.5	1.2	29	16	72	.47	12.0	0.082	2.1	5.75	SST	CG	N
1.100	27.94	72520	2.00	50.8	.930	23.6	17	3.0	1.5	38	26	114	.52	13.2	0.085	2.2	6.13	MW	CG	N
1.100	27.94	72520S	2.00	50.8	.930	23.6	15	2.6	1.2	31	18	80	.52	13.2	0.085	2.2	6.13	SST	CG	N
1.100	27.94	72532	2.00	50.8	.914	23.2	25	4.4	1.4	34	34	150	.58	14.8	0.093	2.4	6.25	MW	CG	N
1.100	27.94	72532S	2.00	50.8	.914	23.2	21	3.7	1.1	27	22	100	.58	14.8	0.093	2.4	6.25	SST	CG	N
1.100	27.94	72543	2.00	50.8	.908	23.1	26	4.6	1.4	35	36	160	.64	16.2	0.096	2.4	6.63	MW	CG	N
1.100	27.94	72543S	2.00	50.8	.908	23.1	22	3.9	1.1	28	25	109	.64	16.2	0.096	2.4	6.63	SST	CG	N
1.100	27.94	72554	2.00	50.8	.890	22.6	36	6.3	1.3	32	46	206	.72	18.3	0.105	2.7	6.88	MW	CG	N
1.100	27.94	72554S	2.00	50.8	.890	22.6	31	5.4	1.0	26	32	142	.72	18.3	0.105	2.7	6.88	SST	CG	N
1.100	27.94	72565	2.00	50.8	.876	22.3	49	8.5	1.2	30	56	251	.77	19.6	0.112	2.8	6.88	MW	CG	N
1.100	27.94	72565S	2.00	50.8	.876	22.3	41	7.2	.89	23	37	164	.77	19.6	0.112	2.8	6.88	SST	CG	N
1.100	27.94	72575	2.00	50.8	.860	21.8	66	12	1.0	27	69	308	.81	20.6	0.120	3.0	6.75	MW	CG	N
1.100	27.94	72575S	2.00	50.8	.860	21.8	56	9.9	.80	20	45	201	.81	20.6	0.120	3.0	6.75	SST	CG	N
1.100	27.94	72587	2.00	50.8	.850	21.6	74	13	1.0	27	78	347	.89	22.6	0.125	3.2	7.13	MW	CG	N
1.100	27.94	72587S	2.00	50.8	.850	21.6	63	11	.80	20	51	227	.89	22.6	0.125	3.2	7.13	S		



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.100	27.94	72521S	2.50	63.5	.930	23.6	12	2.0	1.5	39	18	80	.62	15.7	0.085	2.2	7.25	SST	CG	N
1.100	27.94	72533	2.50	63.5	.914	23.2	20	3.4	1.7	44	34	150	.69	17.4	0.093	2.4	7.38	MW	CG	N
1.100	27.94	72533S	2.50	63.5	.914	23.2	17	2.9	1.4	34	22	100	.69	17.4	0.093	2.4	7.38	SST	CG	N
1.100	27.94	72544	2.50	63.5	.908	23.1	21	3.6	1.7	44	36	161	.76	19.2	0.096	2.4	7.88	MW	CG	N
1.100	27.94	72544S	2.50	63.5	.908	23.1	18	3.1	1.4	35	25	109	.76	19.2	0.096	2.4	7.88	SST	CG	N
1.100	27.94	72555	2.50	63.5	.890	22.6	28	5.0	1.6	41	46	206	.87	22.0	0.105	2.7	8.25	MW	CG	N
1.100	27.94	72555S	2.50	63.5	.890	22.6	24	4.2	1.3	34	32	142	.87	22.0	0.105	2.7	8.25	SST	CG	N
1.100	27.94	72567	2.50	63.5	.876	22.3	38	6.6	1.5	38	56	251	.92	23.5	0.112	2.8	8.25	MW	CG	N
1.100	27.94	72567S	2.50	63.5	.876	22.3	32	5.6	1.1	29	37	164	.92	23.5	0.112	2.8	8.25	SST	CG	N
1.100	27.94	72577	2.50	63.5	.860	21.8	52	9.0	1.3	34	69	308	.98	24.8	0.120	3.0	8.13	MW	CG	N
1.100	27.94	72577S	2.50	63.5	.860	21.8	44	7.7	1.0	26	45	201	.98	24.8	0.120	3.0	8.13	SST	CG	N
1.100	27.94	72589	2.50	63.5	.850	21.6	58	10	1.4	34	78	347	1.08	27.4	0.125	3.2	8.63	MW	CG	N
1.100	27.94	72589S	2.50	63.5	.850	21.6	49	8.6	1.0	26	51	227	1.08	27.4	0.125	3.2	8.63	SST	CG	N
1.100	27.94	72599	2.50	63.5	.830	21.1	76	13	1.3	32	95	423	1.22	30.9	0.135	3.4	9.00	MW	CG	N
1.100	27.94	72599S	2.50	63.5	.830	21.1	65	11	.95	24	61	272	1.22	30.9	0.135	3.4	9.00	SST	CG	N
1.100	27.94	72609	2.50	63.5	.816	20.7	98	17	1.1	29	110	490	1.24	31.6	0.142	3.6	8.75	MW	CG	N
1.100	27.94	72609S	2.50	63.5	.816	20.7	83	15	.85	22	71	316	1.24	31.6	0.142	3.6	8.75	SST	CG	N
1.100	27.94	72620	2.50	63.5	.804	20.4	115	20	1.1	27	124	553	1.31	33.4	0.148	3.8	8.88	MW	CG	N
1.100	27.94	72620S	2.50	63.5	.804	20.4	98	17	.82	21	80	356	1.31	33.4	0.148	3.8	8.88	SST	CG	N
1.100	27.94	72610	2.75	69.9	.816	20.7	88	15	1.3	32	110	490	1.35	34.3	0.142	3.6	9.50	MW	CG	N
1.100	27.94	72610S	2.75	69.9	.816	20.7	75	13	.95	24	71	316	1.35	34.3	0.142	3.6	9.50	SST	CG	N
1.100	27.94	72621	2.75	69.9	.804	20.4	104	18	1.2	30	124	553	1.44	36.7	0.148	3.8	9.75	MW	CG	N
1.100	27.94	72621S	2.75	69.9	.804	20.4	88	15	.91	23	80	356	1.44	36.7	0.148	3.8	9.75	SST	CG	N
1.100	27.94	72511	3.00	76.2	.936	23.8	11	1.9	2.3	57	24	108	.64	16.1	0.082	2.1	7.75	MW	CG	N
1.100	27.94	72511S	3.00	76.2	.936	23.8	9.1	1.6	1.8	45	16	72	.64	16.1	0.082	2.1	7.75	SST	CG	N
1.100	27.94	72522	3.00	76.2	.930	23.6	11	2.0	2.3	58	26	114	.71	18.1	0.085	2.2	8.38	MW	CG	N
1.100	27.94	72522S	3.00	76.2	.930	23.6	9.5	1.7	1.9	48	18	80	.71	18.1	0.085	2.2	8.38	SST	CG	N
1.100	27.94	72534	3.00	76.2	.914	23.2	16	2.8	2.1	54	34	150	.80	20.4	0.093	2.4	8.63	MW	CG	N
1.100	27.94	72534S	3.00	76.2	.914	23.2	14	2.4	1.6	42	22	100	.80	20.4	0.093	2.4	8.63	SST	CG	N
1.100	27.94	72545	3.00	76.2	.908	23.1	17	3.0	2.1	54	36	161	.88	22.3	0.096	2.4	9.13	MW	CG	N
1.100	27.94	72545S	3.00	76.2	.908	23.1	14	2.5	1.7	43	25	109	.88	22.3	0.096	2.4	9.13	SST	CG	N
1.100	27.94	72556	3.00	76.2	.890	22.6	23	4.1	2.0	51	46	206	1.01	25.7	0.105	2.7	9.63	MW	CG	N
1.100	27.94	72556S	3.00	76.2	.890	22.6	20	3.5	1.6	41	32	142	1.01	25.7	0.105	2.7	9.63	SST	CG	N
1.100	27.94	72568	3.00	76.2	.876	22.3	31	5.4	1.8	46	56	251	1.06	27.0	0.112	2.8	9.50	MW	CG	N
1.100	27.94	72568S	3.00	76.2	.876	22.3	26	4.6	1.4	35	37	164	1.06	27.0	0.112	2.8	9.50	SST	CG	N
1.100	27.94	72578	3.00	76.2	.860	21.8	42	7.4	1.6	42	69	308	1.14	29.0	0.120	3.0	9.50	MW	CG	N
1.100	27.94	72578S	3.00	76.2	.860	21.8	36	6.3	1.3	32	45	201	1.14	29.0	0.120	3.0	9.50	SST	CG	N
1.100	27.94	72590	3.00	76.2	.850	21.6	47	8.3	1.7	42	78	347	1.25	31.8	0.125	3.2	10.0	MW	CG	N
1.100	27.94	72590S	3.00	76.2	.850	21.6	40	7.0	1.3	32	51	227	1.25	31.8	0.125	3.2	10.0	SST	CG	N
1.100	27.94	72600	3.00	76.2	.830	21.1	62	11	1.5	39	95	423	1.42	36.0	0.135	3.4	10.5	MW	CG	N
1.100	27.94	72600S	3.00	76.2	.830	21.1	53	9.3	1.2	29	61	272	1.42	36.0	0.135	3.4	10.5	SST	CG	N
1.100	27.94	72611	3.00	76.2	.816	20.7	80	14	1.4	35	110	490	1.46	37.0	0.142	3.6	10.3	MW	CG	N
1.100	27.94	72611S	3.00	76.2	.816	20.7	68	12	1.0	27	71	316	1.46	37.0	0.142	3.6	10.3	SST	CG	N
1.100	27.94	72622	3.00	76.2	.804	20.4	94	16	1.3	34	124	553	1.55	39.5	0.148	3.8	10.5	MW	CG	N
1.100	27.94	72622S	3.00	76.2	.804	20.4	80	14	1.0	25	80	356	1.55	39.5	0.148	3.8	10.5	SST	CG	N
1.100	27.94	72612	3.31	84.1	.816	20.7	64	11	1.6	39	99	442	1.76	44.6	0.142	3.6	12.4	MW	CG	N
1.100	27.94	72612S	3.31	84.1	.816	20.7	54	9.5	1.3	33	71	316	1.76	44.6	0.142	3.6	12.4	SST	CG	N
1.100	27.94	72512	3.50	88.9	.936	23.8	9.1	1.6	2.7	68	24	108	.72	18.2	0.082	2.1	8.75	MW	CG	N
1.100	27.94	72512S	3.50	88.9	.936	23.8	7.7	1.4	2.1	53	16	72	.72	18.2	0.082	2.1	8.75	SST	CG	N
1.100	27.94	72523	3.50	88.9	.930	23.6	9.6	1.7	2.7	68	26	115	.81	20.5	0.085	2.2	9.50	MW	CG	N
1.100	27.94	72523S	3.50	88.9	.930	23.6	8.2	1.4	2.2	56	18	80	.81	20.5	0.085	2.2	9.50	SST	CG	N
1.100	27.94	72535	3.50	88.9	.914	23.2	14	2.4	2.5	63	34	150	.91	23.0	0.093	2.4	9.75	MW	CG	N
1.100	27.94	72535S	3.50	88.9	.914	23.2	12	2.0	1.9	49	22	100	.91	23.0	0.093	2.4	9.75	SST	CG	N
1.100	27.94	72546	3.50	88.9	.908	23.1	14	2.5	2.5	64	36	160	1.00	25.3	0.096	2.4	10.4	MW	CG	N
1.100	27.94	72546S	3.50	88.9	.908	23.1	12	2.1	2.0	51	25	109	1.00	25.3	0.096	2.4	10.4	SST	CG	N
1.100	27.94	72557	3.50	88.9	.890	22.6	20	3.4	2.3	60	46	205	1.16	29.3	0.105	2.7	11.0	MW	CG	N
1.100	27.94	72557S	3.50	88.9	.890	22.6	17	2.9	1.9	49	32	142	1.16	29.3	0.105	2.7	11.0			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.100	27.94	72570S	4.00	101.6	.876	22.3	19	3.4	1.9	48	37	164	1.37	34.8	0.112	2.8	12.3	SST	CG	N
1.100	27.94	72580	4.00	101.6	.860	21.8	31	5.4	2.2	57	69	308	1.47	37.3	0.120	3.0	12.3	MW	CG	N
1.100	27.94	72580S	4.00	101.6	.860	21.8	26	4.6	1.7	44	45	201	1.47	37.3	0.120	3.0	12.3	SST	CG	N
1.100	27.94	72592	4.00	101.6	.850	21.6	34	6.0	2.3	58	78	347	1.63	41.3	0.125	3.2	13.0	MW	CG	N
1.100	27.94	72592S	4.00	101.6	.850	21.6	29	5.1	1.7	44	51	227	1.63	41.3	0.125	3.2	13.0	SST	CG	N
1.100	27.94	72602	4.00	101.6	.830	21.1	45	7.9	2.1	54	95	423	1.86	47.1	0.135	3.4	13.8	MW	CG	N
1.100	27.94	72602S	4.00	101.6	.830	21.1	38	6.7	1.6	41	61	272	1.86	47.1	0.135	3.4	13.8	SST	CG	N
1.100	27.94	72614	4.00	101.6	.816	20.7	59	10	1.9	47	110	490	1.88	47.8	0.142	3.6	13.3	MW	CG	N
1.100	27.94	72614S	4.00	101.6	.816	20.7	50	8.8	1.4	36	71	316	1.88	47.8	0.142	3.6	13.3	SST	CG	N
1.100	27.94	72624	4.00	101.6	.804	20.4	69	12	1.8	46	124	553	2.02	51.2	0.148	3.8	13.6	MW	CG	N
1.100	27.94	72624S	4.00	101.6	.804	20.4	58	10	1.4	35	80	356	2.02	51.2	0.148	3.8	13.6	SST	CG	N
1.100	27.94	72525	4.50	114.3	.930	23.6	7.3	1.3	3.5	89	25	113	1.01	25.6	0.085	2.2	11.9	MW	CG	N
1.100	27.94	72525S	4.50	114.3	.930	23.6	6.2	1.1	2.9	74	18	80	1.01	25.6	0.085	2.2	11.9	SST	CG	N
1.100	27.94	72548	4.50	114.3	.908	23.1	11	1.9	3.3	83	36	161	1.24	31.4	0.096	2.4	12.9	MW	CG	N
1.100	27.94	72548S	4.50	114.3	.908	23.1	9.4	1.7	2.6	66	25	109	1.24	31.4	0.096	2.4	12.9	SST	CG	N
1.100	27.94	72559	4.50	114.3	.890	22.6	15	2.6	3.1	78	46	205	1.44	36.7	0.105	2.7	13.8	MW	CG	N
1.100	27.94	72559S	4.50	114.3	.890	22.6	13	2.2	2.5	64	32	142	1.44	36.7	0.105	2.7	13.8	SST	CG	N
1.100	27.94	72571	4.50	114.3	.876	22.3	20	3.5	2.8	71	56	251	1.53	38.8	0.112	2.8	13.6	MW	CG	N
1.100	27.94	72571S	4.50	114.3	.876	22.3	17	3.0	2.2	55	37	164	1.53	38.8	0.112	2.8	13.6	SST	CG	N
1.100	27.94	72581	4.50	114.3	.860	21.8	27	4.8	2.5	64	69	308	1.64	41.5	0.120	3.0	13.6	MW	CG	N
1.100	27.94	72581S	4.50	114.3	.860	21.8	23	4.1	1.9	49	45	201	1.64	41.5	0.120	3.0	13.6	SST	CG	N
1.100	27.94	72593	4.50	114.3	.850	21.6	30	5.3	2.6	65	78	347	1.81	46.0	0.125	3.2	14.5	MW	CG	N
1.100	27.94	72593S	4.50	114.3	.850	21.6	26	4.5	2.0	50	51	227	1.81	46.0	0.125	3.2	14.5	SST	CG	N
1.100	27.94	72603	4.50	114.3	.830	21.1	39	6.9	2.4	61	95	422	2.09	53.1	0.135	3.4	15.5	MW	CG	N
1.100	27.94	72603S	4.50	114.3	.830	21.1	34	5.9	1.8	46	61	272	2.09	53.1	0.135	3.4	15.5	SST	CG	N
1.100	27.94	72615	4.50	114.3	.816	20.7	51	8.9	2.2	55	110	490	2.13	54.1	0.142	3.6	15.0	MW	CG	N
1.100	27.94	72615S	4.50	114.3	.816	20.7	43	7.6	1.6	42	71	316	2.13	54.1	0.142	3.6	15.0	SST	CG	N
1.100	27.94	72625	4.50	114.3	.804	20.4	61	11	2.1	52	124	553	2.26	57.3	0.148	3.8	15.3	MW	CG	



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.125	28.58	S-931	.97	24.6	1.023	26.0	1.7	.30	.66	17	1.1	5.0	.31	7.8	0.051	1.3	6.00	SST	CG	N
1.125	28.58	11963	.97	24.6	1.003	25.5	4.1	.72	.60	15	2.5	11	.37	9.3	0.061	1.5	6.00	SPR	CG	Z
1.125	28.58	10482	1.00	25.4	.965	24.5	26	4.5	.61	16	16	70	.32	8.1	0.080	2.0	4.00	SPR	CG	N
1.125	28.58	S-1383	1.06	27.0	.915	23.2	57	10	.55	14	31	139	.47	12.0	0.105	2.7	4.50	SST	CG	N
1.125	28.58	3947	1.19	30.2	.941	23.9	31	5.5	.73	18	23	101	.46	11.7	0.092	2.3	5.00	SPR	CG	Z
1.125	28.58	B17-147	1.22	31.0	1.005	25.5	7.7	1.4	.91	23	7.1	31	.24	6.1	0.060	1.5	4.00	SPR	CG	N
1.125	28.58	S-1236	1.25	31.8	.981	24.9	9.6	1.7	.89	23	8.5	38	.36	9.1	0.072	1.8	5.00	SST	CG	N
1.125	28.58	11742	1.25	31.8	.895	22.7	122	21	.35	8.9	43	190	.46	11.7	0.115	2.9	4.00	SPR	CG	Z
1.125	28.58	12271	1.38	34.9	.995	25.3	4.2	.74	.95	24	4.0	18	.42	10.7	0.065	1.7	6.50	SST	CG	N
1.125	28.58	S-147	1.41	35.7	1.031	26.2	.89	.16	1.0	26	.89	4.0	.40	10.1	0.047	1.2	7.50	SST	C	N
1.125	28.58	S-911	1.47	37.3	.981	24.9	7.3	1.3	1.0	26	7.6	34	.43	11.0	0.072	1.8	6.00	SST	CG	N
1.125	28.58	2945	1.50	38.1	1.017	25.8	5.0	.87	1.0	26	5.2	23	.27	6.9	0.054	1.4	4.00	SPR	C	Z
1.125	28.58	12001	1.50	38.1	.935	23.7	27	4.7	.93	24	25	111	.57	14.5	0.095	2.4	6.00	SPR	CG	Z
1.125	28.58	S-1249	1.50	38.1	.915	23.2	48	8.4	.66	17	31	139	.53	13.3	0.105	2.7	5.00	SST	CG	N
1.125	28.58	S-1561	1.50	38.1	.875	22.2	87	15	.57	15	50	222	.69	17.5	0.125	3.2	5.50	SST	CG	N
1.125	28.58	10624	1.56	39.7	.815	20.7	303	53	.32	8.1	97	432	.78	19.7	0.155	3.9	5.00	SPR	CG	Z
1.125	28.58	M-80	1.59	40.5	.859	21.8	115	20	.55	14	64	283	.80	20.3	0.133	3.4	6.00	SPR	CG	Z
1.125	28.58	S-3242	1.72	43.6	1.003	25.5	3.7	.64	1.4	34	5.0	22	.37	9.3	0.061	1.5	6.00	SST	CG	N
1.125	28.58	3302	1.75	44.5	.875	22.2	58	10	.75	19	44	195	1.00	25.4	0.125	3.2	8.00	HD	CG	Z
1.125	28.58	11433	1.88	47.6	.885	22.5	56	9.8	.87	22	48	216	.87	22.1	0.120	3.0	7.25	HD	CG	Z
1.125	28.58	11335	2.00	50.8	.829	21.1	148	26	.59	15	87	387	1.04	26.3	0.148	3.8	7.00	SPR	CG	Z
1.125	28.58	CC-96	2.00	50.8	.805	20.4	210	37	.51	13	107	474	1.12	28.4	0.160	4.1	7.00	SPR	CG	Z
1.125	28.58	S-3239	2.09	53.2	.945	24.0	19	3.3	1.1	27	20	88	.54	13.7	0.090	2.3	6.00	SST	CG	N
1.125	28.58	4340	2.13	54.0	.855	21.7	66	11	.84	21	55	246	1.28	32.6	0.135	3.4	9.50	SPR	CG	Z
1.125	28.58	S-973	2.28	57.9	.965	24.5	8.2	1.4	1.7	43	14	61	.60	15.2	0.080	2.0	7.50	SST	CG	N
1.125	28.58	2694	2.31	58.7	.933	23.7	20	3.6	1.3	32	26	115	.72	18.3	0.096	2.4	7.50	HD	CG	Z
1.125	28.58	S-1569	2.38	60.3	.875	22.2	69	12	.72	18	50	222	.81	20.6	0.125	3.2	6.50	SST	CG	N
1.125	28.58	10483	2.38	60.3	.831	21.1	159	28	.54											



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.140	28.96	11907	1.09	27.8	1.012	25.7	2.9	.50	.58	15	1.7	7.4	.51	13.0	0.064	1.6	8.00	SST	CG	N
1.140	28.96	S-1047	1.25	31.8	.900	22.9	81	14	.54	14	44	194	.60	15.2	0.120	3.0	5.00	SST	CG	N
1.140	28.96	10889	1.31	33.3	1.046	26.6	.79	.14	.94	24	.74	3.3	.38	9.6	0.047	1.2	8.00	SST	CG	N
1.140	28.96	12321	1.50	38.1	1.030	26.2	2.2	.38	1.1	29	2.4	11	.37	9.4	0.055	1.4	6.75	SPR	CG	Z
1.140	28.96	12644	1.83	46.4	1.032	26.2	2.4	.42	1.5	38	3.5	16	.35	8.9	0.054	1.4	5.50	SST	C	N
1.140	28.96	S-3008	1.88	47.6	.880	22.4	99	17	.54	14	53	236	.72	18.2	0.130	3.3	5.50	SST	CG	N
1.140	28.96	S-1203	1.94	49.2	.880	22.4	87	15	.61	16	53	236	.78	19.8	0.130	3.3	6.00	SST	CG	N
1.140	28.96	S-254	2.00	50.8	.756	19.2	352	62	.42	11	147	653	1.47	37.4	0.192	4.9	7.67	SST	CG	N
1.140	28.96	3999	2.25	57.2	.956	24.3	19	3.3	1.2	30	23	100	.62	15.8	0.092	2.3	6.75	SPR	CG	Z
1.140	28.96	11343	2.41	61.1	.844	21.4	157	27	.55	14	86	383	.96	24.4	0.148	3.8	6.50	SPR	CG	Z
1.140	28.96	3173	2.56	65.1	.956	24.3	13	2.2	1.7	44	22	99	.83	21.0	0.092	2.3	9.00	SPR	CG	Z
1.140	28.96	3156	2.63	66.7	1.028	26.1	2.8	.49	2.0	52	5.7	25	.34	8.5	0.056	1.4	6.00	SPR	CG	Z
1.140	28.96	11130	2.84	72.2	.756	19.2	270	47	.63	16	170	758	2.02	51.2	0.192	4.9	10.5	SPR	CG	Z
1.140	28.96	12755	2.84	72.2	.766	19.5	232	41	.77	19	178	790	2.01	51.1	0.187	4.7	10.8	OT	CG	N
1.140	28.96	S-1168	3.00	76.2	.960	24.4	8.9	1.6	2.1	53	19	83	.90	22.9	0.090	2.3	10.0	SST	CG	N
1.140	28.96	11799	3.13	79.4	.830	21.1	124	22	.77	20	96	427	1.40	35.4	0.155	3.9	9.00	SPR	CG	Z
1.140	28.96	10365	3.19	81.0	.844	21.4	76	13	1.1	29	86	383	1.67	42.3	0.148	3.8	11.3	SPR	CG	Z
1.140	28.96	4312	3.88	98.4	.870	22.1	51	8.9	1.3	33	66	292	1.52	38.6	0.135	3.4	11.3	SPR	CG	Z
1.140	28.96	3158	4.00	101.6	.890	22.6	30	5.2	1.8	46	54	240	1.78	45.2	0.125	3.2	14.0	SPR	CG	Z
1.140	28.96	S-1458	4.88	123.8	.970	24.6	5.1	.88	3.5	88	17	78	1.11	28.1	0.085	2.2	13.0	SST	CG	N
1.140	28.96	10571	4.88	123.8	.890	22.6	23	4.1	2.3	59	54	240	2.06	52.4	0.125	3.2	16.5	SPR	CG	Z
1.140	28.96	12179	5.16	131.0	.814	20.7	75	13	1.5	38	111	494	2.69	68.3	0.163	4.1	16.5	SPR	CG	Z
1.140	28.96	10458	5.25	133.4	.968	24.6	6.7	1.2	2.9	73	19	86	1.03	26.2	0.086	2.2	12.0	SPR	CG	Z
1.140	28.96	10376	5.31	134.9	.966	24.5	7.1	1.2	2.8	72	20	89	1.04	26.5	0.087	2.2	12.0	HD	CG	Z
1.140	28.96	3024	5.63	142.9	.786	20.0	88	15	1.6	41	141	628	3.54	89.9	0.177	4.5	20.0	SPR	CG	Z
1.156	29.36	S-262	.50	12.7	1.062	27.0	2.2	.39	.27	6.7	.59	2.6	.24	6.0	0.047	1.2	4.00	SST	C	N
1.156	29.36	3306	.69	17.4	.996	25.3	32	5.5	.33	8.3	10	46	.36	9.1	0.080	2.0	3.50	SPR	C	Z
1.156	29.36	10831	.81	20.6	1.066	27.1	1.9	.33	.59	15	1.1	5.0	.23	5.7	0.045	1.1	4.00	SST	C	N
1.156	29.36	B8-47	.88	22.																




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.172	29.77	1797	2.44	61.9	.902	22.9	66	12	.97	25	64	285	1.15	29.2	0.135	3.4	8.50	HD	CG	Z
1.172	29.77	11862	2.94	74.6	1.016	25.8	9.1	1.6	1.6	39	14	62	.51	12.9	0.078	2.0	6.50	SPR	CG	N
1.172	29.77	B17-188	3.50	88.9	1.082	27.5	.41	.07	3.0	76	1.2	5.4	.50	12.6	0.045	1.1	11.0	SST	CG	N
1.172	29.77	S-1244	3.63	92.1	1.012	25.7	7.9	1.4	1.8	46	14	63	.56	14.2	0.080	2.0	7.00	SST	CG	N
1.172	29.77	3016	4.17	106.0	.888	22.6	49	8.5	1.5	39	74	330	1.85	46.9	0.142	3.6	13.0	SPR	CG	GI
1.172	29.77	3670	4.28	108.7	1.074	27.3	.73	.13	3.7	95	2.7	12	.54	13.7	0.049	1.2	10.0	SPR	CG	Z
1.172	29.77	11220	6.00	152.4	.788	20.0	143	25	1.2	30	166	740	3.17	80.5	0.192	4.9	16.5	SPR	CG	Z
1.172	29.77	S-1616	7.00	177.8	.988	25.1	3.3	.58	4.7	119	15	69	2.30	58.4	0.092	2.3	24.0	SST	CG	N
1.172	29.77	10675	10.8	273.1	.860	21.8	27	4.7	3.5	90	95	424	4.99	126.8	0.156	4.0	32.0	SPR	CG	Z
1.172	29.77	2742	11.3	285.8	.908	23.1	11	2.0	5.2	133	60	267	4.88	124.1	0.132	3.4	36.0	SPR	CG	Z
1.188	30.18	10160	.44	11.1	1.028	26.1	43	7.6	.20	5.0	8.6	38	.24	6.1	0.080	2.0	3.00	SPR	CG	Z
1.188	30.18	10661	.66	16.7	1.000	25.4	86	15	.27	6.9	23	103	.28	7.2	0.094	2.4	3.00	SPR	CG	Z
1.188	30.18	S-3078	.75	19.1	.928	23.6	241	42	.21	5.4	51	227	.42	10.7	0.130	3.3	3.25	SST	CG	N
1.188	30.18	S-3178	.75	19.1	.908	23.1	417	73	.15	3.9	63	282	.42	10.7	0.140	3.6	3.00	SST	CG	N
1.188	30.18	2844	.81	20.6	.808	20.5	1256	220	.13	3.2	159	709	.67	16.9	0.190	4.8	3.50	SPR	CG	Z
1.188	30.18	11918	1.00	25.4	1.066	27.1	4.1	.72	.70	18	2.9	13	.31	7.7	0.061	1.5	5.00	SST	CG	N
1.188	30.18	1902	1.13	28.6	1.038	26.4	6.6	1.2	.60	15	4.0	18	.53	13.3	0.075	1.9	7.00	SPR	CG	Z
1.188	30.18	11632	1.22	31.0	1.006	25.6	15	2.6	.58	15	8.7	39	.64	16.2	0.091	2.3	7.00	SPR	CG	Z
1.188	30.18	12540	1.38	34.9	1.028	26.1	17	3.0	.86	22	15	66	.44	11.2	0.080	2.0	4.50	SPR	CG	N
1.188	30.18	533	1.38	34.9	.978	24.8	50	8.8	.64	16	32	143	.60	15.3	0.105	2.7	4.75	HD	CG	Z
1.188	30.18	11259	1.41	35.7	1.028	26.1	19	3.4	.78	20	15	66	.42	10.7	0.080	2.0	4.25	SPR	CG	Z
1.188	30.18	12334	1.50	38.1	1.032	26.2	9.7	1.7	1.0	26	10	45	.47	11.9	0.078	2.0	6.00	SPR	CG	Z
1.188	30.18	11642	1.50	38.1	1.028	26.1	14	2.5	1.0	26	15	66	.40	10.2	0.080	2.0	5.00	SPR	CG	Z
1.188	30.18	3186	1.50	38.1	.774	19.7	932	163	.22	5.6	204	907	1.04	26.3	0.207	5.3	5.00	SPR	CG	Z
1.188	30.18	1849	1.53	38.9	1.006	25.6	30	5.2	.98	25	29	131	.41	10.4	0.091	2.3	4.50	MW	CG	Z
1.188	30.18	11485	1.59	40.5	1.020	25.9	18	3.1	.97	25	17	77	.50	12.8	0.084	2.1	5.00	SPR	CG	Z
1.188	30.18	S-3058	1.88	47.6	1.068	27.1	3.2	.56	1.5	38	4.8	21	.39	9.9	0.060	1.5	5.50	SST	CG	N
1.188	30.18																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.203	30.56	12087	2.06	52.4	.933	23.7	78	14	.80	20	63	278	.95	24.0	0.135	3.4	7.00	SPR	CG	Z
1.203	30.56	B18-166	2.28	57.9	1.003	25.5	19	3.4	1.4	36	27	122	.75	19.1	0.100	2.5	7.50	SPR	CG	N
1.203	30.56	S-241	2.34	59.5	.963	24.5	45	7.9	.92	23	42	185	.78	19.8	0.120	3.0	6.50	SST	CG	N
1.203	30.56	S-337	2.38	60.3	.993	25.2	23	4.0	1.3	33	29	131	.74	18.7	0.105	2.7	7.00	SST	CG	N
1.203	30.56	10291	2.38	60.3	.907	23.0	98	17	.84	21	82	364	1.18	30.1	0.148	3.8	8.00	SPR	CG	Z
1.203	30.56	S-281	2.38	60.3	.907	23.0	93	16	.79	20	74	328	1.11	28.2	0.148	3.8	7.50	SST	CG	N
1.203	30.56	3626	2.75	69.9	1.113	28.3	.54	.09	2.3	58	1.2	5.5	.45	11.4	0.045	1.1	9.00	HD	C	Z
1.203	30.56	10461	2.75	69.9	.999	25.4	20	3.6	1.4	36	29	130	.79	20.1	0.102	2.6	7.75	SPR	CG	Z
1.203	30.56	12301	3.00	76.2	1.113	28.3	.54	.09	2.6	66	1.4	6.3	.41	10.3	0.045	1.1	9.00	SPR	CG	Z
1.203	30.56	4339	3.25	82.6	.753	19.1	485	85	.51	13	246	1096	2.36	60.0	0.225	5.7	10.5	SPR	CG	Z
1.203	30.56	12090	3.38	85.7	1.079	27.4	1.6	.28	2.8	70	4.4	19	.62	15.7	0.062	1.6	10.0	SST	CG	N
1.203	30.56	12002	3.38	85.7	1.013	25.7	14	2.5	1.6	42	24	105	.76	19.3	0.095	2.4	8.00	SPR	CG	Z
1.203	30.56	B18-201	3.47	88.1	1.061	26.9	2.5	.43	2.7	68	6.7	30	.78	19.8	0.071	1.8	11.0	SST	CG	N
1.203	30.56	S-306	3.50	88.9	1.033	26.2	6.7	1.2	2.5	63	17	74	.85	21.6	0.085	2.2	9.00	SST	C	N
1.203	30.56	2955	3.56	90.5	1.063	27.0	2.5	.44	2.7	68	6.7	30	.88	22.2	0.070	1.8	11.5	SPR	C	Z
1.203	30.56	2548	4.38	111.1	.983	25.0	14	2.4	2.6	65	35	157	1.51	38.4	0.110	2.8	13.8	SPR	CG	Z
1.203	30.56	1745	5.13	130.2	1.079	27.4	.99	.17	4.0	103	4.0	18	1.09	27.6	0.062	1.6	16.5	SPR	C	Z
1.203	30.56	10974	5.88	149.2	.963	24.5	15	2.6	3.1	79	46	202	2.16	54.9	0.120	3.0	18.0	HD	CG	Z
1.203	30.56	11826	7.25	184.2	.991	25.2	8.7	1.5	3.5	88	30	135	1.80	45.8	0.106	2.7	16.0	SST	C	N
1.203	30.56	1551	7.75	196.9	.909	23.1	25	4.4	3.2	81	80	357	3.63	92.1	0.147	3.7	24.7	SPR	CG	Z
1.203	30.56	S-346	16.0	406.4	1.023	26.0	1.6	.29	11	290	19	83	3.56	90.3	0.090	2.3	38.5	SST	C	N
1.219	30.96	11552	.94	23.8	.949	24.1	.02	.003	.88	22	.02	.07	.06	1.5	0.135	3.4	3.50	MW	CG	Z
1.219	30.96	3444	.94	23.8	.943	24.0	275	48	.24	6.1	66	293	.48	12.3	0.138	3.5	3.50	SPR	CG	Z
1.219	30.96	B10-8	1.00	25.4	.969	24.6	119	21	.39	9.9	46	206	.50	12.7	0.125	3.2	4.00	SST	CG	N
1.219	30.96	S-974	1.16	29.4	.979	24.9	104	18	.39	10	41	182	.47	11.8	0.120	3.0	4.00	SST	CG	N
1.219	30.96	12701	1.31	33.3	1.057	26.8	17	2.9	.87	22	15	65	.45	11.3	0.081	2.1	4.50	SPR	C	N
1.219	30.96	10875	1.31	33.3	1.009	25.6	28	4.9	.68	17	19	85	.63	16.0	0.105	2.7	6.00	SST	CG	N
1.219	30.96	10704	1.38	34.9	1.075	27.3	9.1	1.6	1.1	27	9.5	42	.32	8.2	0.072	1.8	4.50	SST	CG	N
1.219	30.96	12631	1.38	34.9	1.059	26.9	16	2.8	.91	23	15	65	.44	11.2	0.080	2.0	4.50	HD	C	N
1.219	30.96	11353	1.38	34.9	.895	22.7	297	52	.31	7.8	91	406	.73	18.5	0.162	4.1	4.50	SST	CG	N
1.219	30.96	3451	1.44	36.5	1.035	26.3	36	6.3	.59	15	21	94	.37	9.3	0.092	2.3	4.00	HD	CG	Z
1.219	30.96	2885	1.53	38.9	1.017	25.8	37	6.5	.75	19	28	124	.49	12.5	0.101	2.6	5.00	SPR	CG	Z
1.219	30.96	11164	1.63	41.3	.907	23.0	236	41	.39	9.9	92	409	.78	19.8	0.156	4.0	5.00	SPR	CG	Z
1.219	30.96	KK-71	1.75	44.5	1.039	26.4	29	5.1	.63	16	18	82	.36	9.1	0.090	2.3	4.00	SST	CG	N
1.219	30.96	10304	1.75	44.5	1.009	25.6	32	5.5	.99	25	31	139	.74	18.7	0.105	2.7	6.00	SPR	C	Z
1.219	30.96	12096	1.75	44.5	.859	21.8	384	67	.35	8.8	133	593	.99	25.1	0.180	4.6	5.50	SPR	CG	Z
1.219	30.96	11120	1.97	50.0	.879	22.3	198	35	.60	15	118	526	1.23	31.3	0.170	4.3	7.25	SPR	CG	Z
1.219	30.96	11579	2.22	56.4	.951	24.2	60	11	1.0	25	60	269	1.21	30.6	0.134	3.4	8.00	SPR	CG	N
1.219	30.96	4391	2.33	59.1	.923	23.4	94	16	.86	22	81	360	1.18	30.1	0.148	3.8	8.00	SPR	CG	Z
1.219	30.96	S-955	2.34	59.5	1.035	26.3	14	2.4	1.4	36	20	87	.60	15.2	0.092	2.3	6.50	SST	CG	N
1.219	30.96	S-1336	2.38	60.3	1.037	26.3	14	2.4	1.4	36	19	85	.68	17.3	0.091	2.3	6.50	SST	C	N
1.219	30.96	11320	2.38	60.3	.907	23.0	177	31	.52	13	92	409	.94	23.8	0.156	4.0	6.00	SPR	CG	Z
1.219	30.96	B18-194	2.44	61.9	1.129	28.7	.52	.09	2.0	52	1.1	4.7	.41	10.3	0.045	1.1	9.00	SPR	CG	N
1.219	30.96	11932	2.50	63.5	.829	21.1	387	68	.43	11	168	747	1.37	34.7	0.195	5.0	7.00	SPR	CG	N
1.219	30.96	3404	2.75	69.9	1.009	25.6	23	4.0	1.4	35	31	139	.86	21.7	0.105	2.7	8.00	SPR	CG	Z
1.219	30.96	S-3053	2.88	73.0	1.075	27.3	5.6	.97	1.8	46	10	44	.50	12.8	0.072	1.8	6.00	SST	C	N
1.219	30.96	12328	3.00	76.2	1.119	28.4	1.0	.18	2.6	65	2.6	12	.43	10.8	0.050	1.3	7.50	SPR	C	Z
1.219	30.96	S-1375	3.00	76.2	1.117	28.4	.59	.10	2.4	61	1.4	6.3	.61	15.5	0.051	1.3	11.0	SST	C	N
1.219	30.96	B18-182	3.22	81.8	.725	18.4	574	101	.47	12	267	1188	2.72	69.0	0.247	6.3	11.0	SST	CG	N
1.219	30.96	4302	3.25	82.6	1.009	25.6	16	2.8	2.0	50	31	139	1.05	26.7	0.105	2.7	10.0	SPR	CG	Z
1.219	30.96	11858	3.84	97.6	1.043	26.5	7.6	1.3	2.4	61	18	81	.79	20.1	0.088	2.2	9.00	SST	CG	N
1.219	30.96	7056	4.00	101.6	.865	22.0	99	17	1.2	30	118	525	2.48	62.9	0.177	4.5	13.0	SST	C	N
1.219	30.96	10989	4.06	103.2	.805	20.4	255	45	.78	20	199	887	2.48	63.1	0.207	5.3	12.0	HD	CG	Z
1.219	30.96	283	4.50	114.3	.895	22.7	70	12	1.5	37	103	457	2.27	57.6	0.162	4.1	14.0	HD	CG	Z
1.219	30.96	11731	7.50	190.5	.895	22.7	41	7.2	2.5	64	103	457	3.65	92.6	0.162	4.1	22.5	SPR	CG	Z
1.219	30.96	2841	7.75	196.9	.923	23.4	24	4.2	3.4	86	81	360	3.77	95.9	0.148	3.8	25.5	HD	CG	Z
1.219	30.96	4174	12.0	304.8	1.039	26.4	3.0	.52	6.7	169	20	88	2.25	57.2	0.090	2.3	24.0	SPR	C	Z
1.225	31.12	72627	.88	22.4	1.055	26.8	37	6.4	.59	15	22	97	.29	7.3	0.085	2.2	3.38	MW	CG	N
1.225	31.12	72627S	.88	22.4	1.055	26.8	31	5.4	.52	13	16	72	.29	7.3	0.085	2.2	3.38	SST	CG	N
1.225	31.12	72637	.88	22.4	1.033	26.2	60	10	.56	14	33	147	.32	8.2	0.096	2.4	3.38	MW	CG	N
1.225	31.12	72637S	.88	22.4	1.033	26.2	51	8.9	.44	11	22	99	.32	8.2	0.096	2.4	3.38	SST	CG	N
1.225	31.12	72651	.88	22.4	1.015	25.8	83	14	.51	13	42	188	.37	9.3	0.105	2.7	3.50	MW	CG	N
1.225	31.12	72651S	.88	22.4	1.015	25.8	70	12	.41	10	29	129	.37	9.3	0.105	2.7	3.50	SST	CG	N
1.225	31.12	72664	.88	22.4	1.001	25.4	105													



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.225	31.12	72680S	1.00	25.4	.975	24.8	114	20	.40	10	46	205	.50	12.7	0.125	3.2	4.00	SST	CG	N
1.225	31.12	72694	1.00	25.4	.955	24.3	183	32	.46	12	84	375	.54	13.7	0.135	3.4	4.00	MW	CG	N
1.225	31.12	72694S	1.00	25.4	.955	24.3	156	27	.36	9.0	55	246	.54	13.7	0.135	3.4	4.00	SST	CG	N
1.225	31.12	72709	1.00	25.4	.929	23.6	270	47	.41	10	110	489	.59	15.0	0.148	3.8	4.00	MW	CG	N
1.225	31.12	72709S	1.00	25.4	.929	23.6	229	40	.32	8.0	73	322	.59	15.0	0.148	3.8	4.00	SST	CG	N
1.225	31.12	72729	1.00	25.4	.901	22.9	415	73	.35	8.8	143	637	.65	16.5	0.162	4.1	4.00	MW	CG	N
1.225	31.12	72729S	1.00	25.4	.901	22.9	352	62	.26	6.5	91	404	.65	16.5	0.162	4.1	4.00	SST	CG	N
1.225	31.12	72639	1.25	31.8	1.033	26.2	39	6.7	.84	21	32	144	.41	10.4	0.096	2.4	4.25	MW	CG	N
1.225	31.12	72639S	1.25	31.8	1.033	26.2	33	5.7	.68	17	22	99	.41	10.4	0.096	2.4	4.25	SST	CG	N
1.225	31.12	72653	1.25	31.8	1.015	25.8	53	9.2	.79	20	42	186	.46	11.7	0.105	2.7	4.38	MW	CG	N
1.225	31.12	72653S	1.25	31.8	1.015	25.8	45	7.9	.64	16	29	129	.46	11.7	0.105	2.7	4.38	SST	CG	N
1.225	31.12	72666	1.25	31.8	1.001	25.4	67	12	.75	19	50	221	.50	12.8	0.112	2.8	4.50	MW	CG	N
1.225	31.12	72666S	1.25	31.8	1.001	25.4	57	9.9	.59	15	33	148	.50	12.8	0.112	2.8	4.50	SST	CG	N
1.225	31.12	72681	1.25	31.8	.975	24.8	101	18	.67	17	68	301	.58	14.7	0.125	3.2	4.63	MW	CG	N
1.225	31.12	72681S	1.25	31.8	.975	24.8	86	15	.54	14	46	205	.58	14.7	0.125	3.2	4.63	SST	CG	N
1.225	31.12	72695	1.25	31.8	.955	24.3	136	24	.61	15	83	369	.64	16.3	0.135	3.4	4.75	MW	CG	N
1.225	31.12	72695S	1.25	31.8	.955	24.3	116	20	.48	12	55	246	.64	16.3	0.135	3.4	4.75	SST	CG	N
1.225	31.12	72710	1.25	31.8	.929	23.6	199	35	.55	14	109	484	.70	17.9	0.148	3.8	4.75	MW	CG	N
1.225	31.12	72710S	1.25	31.8	.929	23.6	169	30	.43	11	73	322	.70	17.9	0.148	3.8	4.75	SST	CG	N
1.225	31.12	72629	1.50	38.1	1.055	26.8	19	3.4	1.1	28	21	96	.39	10.0	0.085	2.2	4.63	MW	CG	N
1.225	31.12	72629S	1.50	38.1	1.055	26.8	16	2.9	.99	25	16	72	.39	10.0	0.085	2.2	4.63	SST	CG	N
1.225	31.12	72640	1.50	38.1	1.033	26.2	31	5.4	1.0	27	32	144	.46	11.6	0.096	2.4	4.75	MW	CG	N
1.225	31.12	72640S	1.50	38.1	1.033	26.2	26	4.6	.84	21	22	99	.46	11.6	0.096	2.4	4.75	SST	CG	N
1.225	31.12	72654	1.50	38.1	1.015	25.8	43	7.4	.99	25	42	187	.51	13.0	0.105	2.7	4.88	MW	CG	N
1.225	31.12	72654S	1.50	38.1	1.015	25.8	36	6.3	.80	20	29	129	.51	13.0	0.105	2.7	4.88	SST	CG	N
1.225	31.12	72667	1.50	38.1	1.001	25.4	54	9.4	.94	24	50	224	.56	14.2	0.112	2.8	5.00	MW	CG	N
1.225	31.12	72667S	1.50	38.1	1.001	25.4	46	8.0	.73	19	33	148	.56	14.2	0.112	2.8	5.00	SST	CG	N
1.225	31.12	72682	1.50	38.1	.975	24.8	81	14	.84	21	68	302	.66	16.7	0.125	3.2	5.25	MW	CG	N
1.225	31.12	72682S	1.50	38.1	.975	24.8	69	12	.67	17	46	205	.66	16.7	0.125	3.2	5.25	SST	CG	N
1.225	31.12	72696	1.50	38.1	.955	24.3	116	20	.74	19	86	383	.69	17.6	0.135	3.4	5.13	MW	CG	N
1.225	31.12	72696S	1.50	38.1	.955	24.3	98	17	.56	14	55	246	.69	17.6	0.135	3.4	5.13	SST	CG	N
1.225	31.12	72711	1.50	38.1	.929	23.6	158	28	.69	17	108	481	.81	20.7	0.148	3.8	5.50	MW	CG	N
1.225	31.12	72711S	1.50	38.1	.929	23.6	134	23	.54	14	73	322	.81	20.7	0.148	3.8	5.50	SST	CG	N
1.225	31.12	72730	1.50	38.1	.901	22.9	238	42	.60	15	143	637	.89	22.6	0.162	4.1	5.50	MW	CG	N
1.225	31.12	72730S	1.50	38.1	.901	22.9	203	35	.45	11	91	404	.89	22.6	0.162	4.1	5.50	SST	CG	N
1.225	31.12	72743	1.50	38.1	.871	22.1	353	62	.52	13	185	824	.97	24.7	0.177	4.5	5.50	MW	CG	N
1.225	31.12	72743S	1.50	38.1	.871	22.1	300	53	.39	9.9	118	523	.97	24.7	0.177	4.5	5.50	SST	CG	N
1.225	31.12	72751	1.50	38.1	.841	21.4	516	90	.44	11	226	1005	1.03	26.2	0.192	4.9	5.38	MW	CG	N
1.225	31.12	72751S	1.50	38.1	.841	21.4	439	77	.31	8.0	138	613	1.03	26.2	0.192	4.9	5.38	SST	CG	N
1.225	31.12	72641	1.75	44.5	1.033	26.2	26	4.6	1.2	32	33	145	.50	12.8	0.096	2.4	5.25	MW	CG	N
1.225	31.12	72641S	1.75	44.5	1.033	26.2	22	3.9	1.0	25	22	99	.50	12.8	0.096	2.4	5.25	SST	CG	N
1.225	31.12	72656	1.75	44.5	1.015	25.8	37	6.5	1.2	30	44	194	.56	14.3	0.105	2.7	5.38	MW	CG	N
1.225	31.12	72656S	1.75	44.5	1.015	25.8	31	5.5	.92	23	29	129	.56	14.3	0.105	2.7	5.38	SST	CG	N
1.225	31.12	72669	1.75	44.5	1.001	25.4	51	8.9	1.0	25	51	227	.59	14.9	0.112	2.8	5.25	MW	CG	N
1.225	31.12	72669S	1.75	44.5	1.001	25.4	43	7.6	.77	19	33	148	.59	14.9	0.112	2.8	5.25	SST	CG	N
1.225	31.12	72683	1.75	44.5	.975	24.8	67	12	1.0	26	68	304	.73	18.7	0.125	3.2	5.88	MW	CG	N
1.225	31.12	72683S	1.75	44.5	.975	24.8	57	10	.81	20	46	205	.73	18.7	0.125	3.2	5.88	SST	CG	N
1.225	31.12	72698	1.75	44.5	.955	24.3	92	16	.93	24	86	383	.81	20.6	0.135	3.4	6.00	MW	CG	N
1.225	31.12	72698S	1.75	44.5	.955	24.3	78	14	.71	18	55	246	.81	20.6	0.135	3.4	6.00	SST	CG	N
1.225	31.12	72713	1.75	44.5	.929	23.6	134	23	.84	21	113	501	.91	23.0	0.148	3.8	6.13	MW	CG	N
1.225	31.12	72713S	1.75	44.5	.929	23.6	114	20	.64	16	73	322	.91	23.0	0.148	3.8	6.13	SST	CG	N
1.225	31.12	72630	2.00	50.8	1.055	26.8	14	2.5	1.5	39	21	95	.48	12.1	0.085	2.2	5.63	MW	CG	N
1.225	31.12	72630S	2.00	50.8	1.055	26.8	12	2.1	1.4	34	16	72	.48	12.1	0.085	2.2	5.63	SST	CG	N
1.225	31.12	72642	2.00	50.8	1.033	26.2	23	3.9	1.4	37	33	145	.55	14.0	0.096	2.4	5.75	MW	CG	N
1.225	31.12	72642S	2.00	50.8	1.033	26.2	19	3.3	1.2	29	22	99	.55	14.0	0.096	2.4	5.75	SST	CG	N
1.225	31.12	72657	2.00	50.8	1.015	25.8	31	5.4	1.4	35	42	187	.63	16.0	0.105	2.7	6.00	MW	CG	N
1.225	31.12	72657S	2.00	50.8	1.015	25.8	26	4.6	1.1	28	29	129	.63	16.0	0.105	2.7	6.00	SST	CG	N
1.225	31.12	72670	2.00	50.8	1.001	25.4	39	6.7	1.3	33	50	223	.70	17.8	0.112	2.8	6.25	MW	CG	N
1.225	31.12	72670S	2.00	50.8	1.001	25.4	33	5.7	1.0	26	33	148	.70	17.8	0.112	2.8	6.25	SST	CG	N
1.225	31.12	72684	2.00	50.8	.975	24.8	58	10	1.2	30	68	300	.83	21.0	0.125	3.2	6.63	MW	CG	N
1.225	31.12	72684S	2.00	50.8	.975	24.8	49	8.6	.94	24	46	205	.83	21.0	0.125	3.2	6.63	SST	CG	N
1.225	31.12	72699	2.00	50.8	.955	24.3	82	14	1.0	27	86	383	.88	22.3	0.135	3.4	6.50	MW	CG	N
1.225	31.12	72699S	2.00	50.8	.955	24.3	70	12	.79	20	55	246	.88	22.3	0.135	3.4	6.50	SST	CG	N
1.225	31.12																			



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.225	31.12	72732S	2.25	57.2	.901	22.9	128	22	.71	18	91	404	1.22	30.9	0.162	4.1	7.50	SST	CG	N
1.225	31.12	72631	2.50	63.5	1.055	26.8	11	1.9	1.9	49	21	96	.56	14.3	0.085	2.2	6.63	MW	CG	N
1.225	31.12	72631S	2.50	63.5	1.055	26.8	9.4	1.7	1.7	44	16	72	.56	14.3	0.085	2.2	6.63	SST	CG	N
1.225	31.12	72644	2.50	63.5	1.033	26.2	18	3.1	1.8	47	32	144	.66	16.8	0.096	2.4	6.88	MW	CG	N
1.225	31.12	72644S	2.50	63.5	1.033	26.2	15	2.6	1.5	38	22	99	.66	16.8	0.096	2.4	6.88	SST	CG	N
1.225	31.12	72658	2.50	63.5	1.015	25.8	24	4.2	1.8	44	42	187	.75	19.0	0.105	2.7	7.13	MW	CG	N
1.225	31.12	72658S	2.50	63.5	1.015	25.8	20	3.6	1.4	36	29	129	.75	19.0	0.105	2.7	7.13	SST	CG	N
1.225	31.12	72671	2.50	63.5	1.001	25.4	30	5.3	1.7	42	50	222	.84	21.3	0.112	2.8	7.50	MW	CG	N
1.225	31.12	72671S	2.50	63.5	1.001	25.4	26	4.5	1.3	33	33	148	.84	21.3	0.112	2.8	7.50	SST	CG	N
1.225	31.12	72686	2.50	63.5	.975	24.8	45	7.8	1.5	38	68	302	.98	25.0	0.125	3.2	7.88	MW	CG	N
1.225	31.12	72686S	2.50	63.5	.975	24.8	38	6.7	1.2	31	46	205	.98	25.0	0.125	3.2	7.88	SST	CG	N
1.225	31.12	72700	2.50	63.5	.955	24.3	64	11	1.3	34	86	383	1.05	26.6	0.135	3.4	7.75	MW	CG	N
1.225	31.12	72700S	2.50	63.5	.955	24.3	54	9.5	1.0	26	55	246	1.05	26.6	0.135	3.4	7.75	SST	CG	N
1.225	31.12	72715	2.50	63.5	.929	23.6	86	15	1.3	32	109	483	1.24	31.5	0.148	3.8	8.38	MW	CG	N
1.225	31.12	72715S	2.50	63.5	.929	23.6	73	13	.99	25	73	322	1.24	31.5	0.148	3.8	8.38	SST	CG	N
1.225	31.12	72722	2.50	63.5	.913	23.2	113	20	1.1	29	128	571	1.27	32.2	0.156	4.0	8.13	MW	CG	N
1.225	31.12	72722S	2.50	63.5	.913	23.2	96	17	.85	22	81	362	1.27	32.2	0.156	4.0	8.13	SST	CG	N
1.225	31.12	72733	2.50	63.5	.901	22.9	131	23	1.1	28	143	637	1.34	33.9	0.162	4.1	8.25	MW	CG	N
1.225	31.12	72733S	2.50	63.5	.901	22.9	111	19	.82	21	91	404	1.34	33.9	0.162	4.1	8.25	SST	CG	N
1.225	31.12	72745	2.50	63.5	.871	22.1	189	33	.98	25	185	824	1.50	38.2	0.177	4.5	8.50	MW	CG	N
1.225	31.12	72745S	2.50	63.5	.871	22.1	160	28	.73	19	118	523	1.50	38.2	0.177	4.5	8.50	SST	CG	N
1.225	31.12	72753	2.50	63.5	.841	21.4	272	48	.83	21	226	1005	1.63	41.5	0.192	4.9	8.50	MW	CG	N
1.225	31.12	72753S	2.50	63.5	.841	21.4	231	41	.60	15	138	613	1.63	41.5	0.192	4.9	8.50	SST	CG	N
1.225	31.12	72760	2.50	63.5	.811	20.6	384	67	.73	19	281	1248	1.76	44.7	0.207	5.3	8.50	MW	CG	N
1.225	31.12	72760S	2.50	63.5	.811	20.6	326	57	.52	13	171	761	1.76	44.7	0.207	5.3	8.50	SST	CG	N
1.225	31.12	72645	2.75	69.9	1.033	26.2	16	2.8	2.0	52	32	144	.71	18.0	0.096	2.4	7.38	MW	CG	N
1.225	31.12	72645S	2.75	69.9	1.033	26.2	14	2.4	1.6	42	22	99	.71	18.0	0.096	2.4	7.38	SST	CG	N
1.225	31.12	72687	2.75	69.9	.975	24.8	40	7.1	1.7	43	68	302	1.06	27.0	0.125	3.2	8.50	MW	CG	N
1.225	31.12	72687S	2.75	69.9	.975	24.8	34	6.0	1.3	34	46	205	1.06	27.0	0.125	3.2	8.50	SST	CG	N
1.225	31.12	72632	3.00	76.2	1.055	26.8	9.1	1.6	2.4	60	21	95	.65	16.5	0.085	2.2	7.63	MW	CG	N
1.225	31.12	72632S	3.00	76.2	1.055	26.8	7.7	1.4	2.1	53	16	72	.65	16.5	0.085	2.2	7.63	SST	CG	N
1.225	31.12	72646	3.00	76.2	1.033	26.2	15	2.5	2.2	57	33	145	.76	19.2	0.096	2.4	7.88	MW	CG	N
1.225	31.12	72646S	3.00	76.2	1.033	26.2	12	2.2	1.8	46	22	99	.76	19.2	0.096	2.4	7.88	SST	CG	N
1.225	31.12	72659	3.00	76.2	1.015	25.8	20	3.4	2.1	54	42	186	.88	22.3	0.105	2.7	8.38	MW	CG	N
1.225	31.12	72659S	3.00	76.2	1.015	25.8	17	2.9	1.7	44	29	129	.88	22.3	0.105	2.7	8.38	SST	CG	N
1.225	31.12	72672	3.00	76.2	1.001	25.4	25	4.3	2.0	52	50	223	.97	24.5	0.112	2.8	8.63	MW	CG	N
1.225	31.12	72672S	3.00	76.2	1.001	25.4	21	3.7	1.6	40	33	148	.97	24.5	0.112	2.8	8.63	SST	CG	N
1.225	31.12	72688	3.00	76.2	.975	24.8	37	6.4	1.9	47	68	304	1.14	29.0	0.125	3.2	9.13	MW	CG	N
1.225	31.12	72688S	3.00	76.2	.975	24.8	31	5.5	1.5	37	46	205	1.14	29.0	0.125	3.2	9.13	SST	CG	N
1.225	31.12	72701	3.00	76.2	.955	24.3	52	9.1	1.6	42	86	383	1.23	31.3	0.135	3.4	9.13	MW	CG	N
1.225	31.12	72701S	3.00	76.2	.955	24.3	44	7.8	1.2	32	55	246	1.23	31.3	0.135	3.4	9.13	SST	CG	N
1.225	31.12	72716	3.00	76.2	.929	23.6	70	12	1.5	39	108	480	1.46	37.1	0.148	3.8	9.88	MW	CG	N
1.225	31.12	72716S	3.00	76.2	.929	23.6	60	10	1.2	31	73	322	1.46	37.1	0.148	3.8	9.88	SST	CG	N
1.225	31.12	72723	3.00	76.2	.913	23.2	93	16	1.4	35	128	571	1.48	37.6	0.156	4.0	9.50	MW	CG	N
1.225	31.12	72723S	3.00	76.2	.913	23.2	79	14	1.0	26	81	362	1.48	37.6	0.156	4.0	9.50	SST	CG	N
1.225	31.12	72734	3.00	76.2	.901	22.9	107	19	1.3	34	143	637	1.56	39.6	0.162	4.1	9.63	MW	CG	N
1.225	31.12	72734S	3.00	76.2	.901	22.9	91	16	1.0	25	91	404	1.56	39.6	0.162	4.1	9.63	SST	CG	N
1.225	31.12	72746	3.00	76.2	.871	22.1	153	27	1.2	31	185	824	1.77	45.0	0.177	4.5	10.0	MW	CG	N
1.225	31.12	72746S	3.00	76.2	.871	22.1	130	23	.90	23	118	523	1.77	45.0	0.177	4.5	10.0	SST	CG	N
1.225	31.12	72754	3.00	76.2	.841	21.4	220	39	1.0	26	226	1005	1.92	48.8	0.192	4.9	10.0	MW	CG	N
1.225	31.12	72754S	3.00	76.2	.841	21.4	187	33	.74	19	138	613	1.92	48.8	0.192	4.9	10.0	SST	CG	N
1.225	31.12	72761	3.00	76.2	.811	20.6	310	54	.90	23	280	1245	2.10	53.2	0.207	5.3	10.1	MW	CG	N
1.225	31.12	72761S	3.00	76.2	.811	20.6	263	46	.65	17	171	761	2.10	53.2	0.207	5.3	10.1	SST	CG	N
1.225	31.12	72633	3.50	88.9	1.055	26.8	7.8	1.4	2.8	71	22	96	.72	18.4	0.085	2.2	8.50	MW	CG	N
1.225	31.12	72633S	3.50	88.9	1.055	26.8	6.6	1.2	2.5	62	16	72	.72	18.4	0.085	2.2	8.50	SST	CG	N
1.225	31.12	72647	3.50	88.9	1.033	26.2	12	2.2	2.6	67	33	145	.85	21.6	0.096	2.4	8.88	MW	CG	N
1.225	31.12	72647S	3.50	88.9	1.033	26.2	10	1.8	2.1	54	22	99	.85	21.6	0.096	2.4	8.88	SST	CG	N
1.225	31.12	72660	3.50	88.9	1.015	25.8	17	2.9	2.5	64	42	186	1.00	25.3	0.105	2.7	9.50	MW	CG	N
1.225	31.12	72660S	3.50	88.9	1.015	25.8	14	2.5	2.0	52	29	129	1.00	25.3	0.105	2.7	9.50	SST	CG	N
1.225	31.12	72673	3.50	88.9	1.001	25.4	21	3.7	2.4	61	50	223	1.11	28.1	0.112	2.8	9.88	MW	CG	N
1.225	31.12	72673S	3.50	88.9	1.001	25.4	18	3.1	1.9	48	33	148	1.11	28.1	0.112	2.8	9.88	SST	CG	N
1.225	31.12	72689	3.50	88.9	.975	24.8	31	5.4	2.2	56	68	302	1.31	33.3	0.125	3.2	10.5	MW	CG	N
1.225	31.12	72689S	3.50	88.9	.975	24.8	26	4.6	1.7	44	46	205	1.31	33.3	0.125	3.2	10.5	SST	CG	N
1.225	31.12	72702	3.50	88.9</																




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.225	31.12	72736S	3.75	95.3	.901	22.9	72	13	1.3	32	91	404	1.90	48.3	0.162	4.1	11.8	SST	CG	N
1.225	31.12	72634	4.00	101.6	1.055	26.8	6.7	1.2	3.2	81	21	95	.81	20.5	0.085	2.2	9.50	MW	CG	N
1.225	31.12	72634S	4.00	101.6	1.055	26.8	5.7	1.0	2.9	73	16	72	.81	20.5	0.085	2.2	9.50	SST	CG	N
1.225	31.12	72648	4.00	101.6	1.033	26.2	11	1.9	3.1	78	33	145	.95	24.1	0.096	2.4	9.88	MW	CG	N
1.225	31.12	72648S	4.00	101.6	1.033	26.2	9.1	1.6	2.4	62	22	99	.95	24.1	0.096	2.4	9.88	SST	CG	N
1.225	31.12	72661	4.00	101.6	1.015	25.8	15	2.5	2.9	73	42	186	1.12	28.3	0.105	2.7	10.6	MW	CG	N
1.225	31.12	72661S	4.00	101.6	1.015	25.8	12	2.2	2.3	60	29	129	1.12	28.3	0.105	2.7	10.6	SST	CG	N
1.225	31.12	72674	4.00	101.6	1.001	25.4	18	3.2	2.8	70	50	222	1.25	31.6	0.112	2.8	11.1	MW	CG	N
1.225	31.12	72674S	4.00	101.6	1.001	25.4	15	2.7	2.2	55	33	148	1.25	31.6	0.112	2.8	11.1	SST	CG	N
1.225	31.12	72690	4.00	101.6	.975	24.8	27	4.7	2.5	64	68	303	1.47	37.3	0.125	3.2	11.8	MW	CG	N
1.225	31.12	72690S	4.00	101.6	.975	24.8	23	4.0	2.0	51	46	205	1.47	37.3	0.125	3.2	11.8	SST	CG	N
1.225	31.12	72703	4.00	101.6	.955	24.3	41	7.1	2.1	54	86	383	1.50	38.1	0.135	3.4	11.1	MW	CG	N
1.225	31.12	72703S	4.00	101.6	.955	24.3	34	6.0	1.6	41	55	246	1.50	38.1	0.135	3.4	11.1	SST	CG	N
1.225	31.12	72718	4.00	101.6	.929	23.6	51	9.0	2.1	54	108	481	1.89	47.9	0.148	3.8	12.8	MW	CG	N
1.225	31.12	72718S	4.00	101.6	.929	23.6	44	7.6	1.7	42	73	322	1.89	47.9	0.148	3.8	12.8	SST	CG	N
1.225	31.12	72726	4.00	101.6	.913	23.2	68	12	1.9	48	128	571	1.91	48.5	0.156	4.0	12.3	MW	CG	N
1.225	31.12	72726S	4.00	101.6	.913	23.2	58	10	1.4	36	81	362	1.91	48.5	0.156	4.0	12.3	SST	CG	N
1.225	31.12	72737	4.00	101.6	.901	22.9	78	14	1.8	47	143	637	2.05	51.9	0.162	4.1	12.6	MW	CG	N
1.225	31.12	72737S	4.00	101.6	.901	22.9	66	12	1.4	35	91	404	2.05	51.9	0.162	4.1	12.6	SST	CG	N
1.225	31.12	72748	4.00	101.6	.871	22.1	111	19	1.7	42	185	824	2.30	58.4	0.177	4.5	13.0	MW	CG	N
1.225	31.12	72748S	4.00	101.6	.871	22.1	94	17	1.2	32	118	523	2.30	58.4	0.177	4.5	13.0	SST	CG	N
1.225	31.12	72756	4.00	101.6	.841	21.4	159	28	1.4	36	226	1005	2.52	64.0	0.192	4.9	13.1	MW	CG	N
1.225	31.12	72756S	4.00	101.6	.841	21.4	135	24	1.0	26	138	613	2.52	64.0	0.192	4.9	13.1	SST	CG	N
1.225	31.12	72763	4.00	101.6	.811	20.6	223	39	1.3	32	281	1248	2.74	69.7	0.207	5.3	13.3	MW	CG	N
1.225	31.12	72763S	4.00	101.6	.811	20.6	190	33	.90	23	171	761	2.74	69.7	0.207	5.3	13.3	SST	CG	N
1.225	31.12	72635	4.50	114.3	1.055	26.8	6.0	1.1	3.6	92	22	96	.89	22.7	0.085	2.2	10.5	MW	CG	N
1.225	31.12	72635S	4.50	114.3	1.055	26.8	5.1	.89	3.2	81	16	72	.89	22.7	0.085	2.2	10.5	SST	CG	N
1.225	31.12	72649	4.50	114.3	1.033	26.2	9.5	1.7	3.5	88	33	146	1.04	26.5	0.096	2.4	10.9	MW	CG	N
1.225	31.12	72649S	4.50	114.3	1.033	26.2	8.1	1.4	2.7	70	22	99	1.04	26.5	0.096	2.4	10.9	SST	CG	N
1.225	31.12	72662	4.50	114.3	1.015	25.8	13	2.2	3.3	83	42	186	1.23	31.3	0.105	2.7	11.8	MW	CG	N
1.225	31.12	72662S	4.50	114.3	1.015	25.8	11	1.9	2.7	67	29	129	1.23	31.3	0.105	2.7	11.8	SST	CG	N
1.225	31.12	72676	4.50	114.3	1.001	25.4	18	3.2	2.8	71	51	227	1.23	31.3	0.112	2.8	11.0	MW	CG	N
1.225	31.12	72676S	4.50	114.3	1.001	25.4	15	2.7	2.2	55	33	148	1.23	31.3	0.112	2.8	11.0	SST	CG	N
1.225	31.12	72691	4.50	114.3	.975	24.8	24	4.2	2.9	73	68	301	1.64	41.7	0.125	3.2	13.1	MW	CG	N
1.225	31.12	72691S	4.50	114.3	.975	24.8	20	3.5	2.3	58	46	205	1.64	41.7	0.125	3.2	13.1	SST	CG	N
1.225	31.12	72705	4.50	114.3	.955	24.3	32	5.7	2.7	68	86	383	1.81	45.9	0.135	3.4	13.4	MW	CG	N
1.225	31.12	72705S	4.50	114.3	.955	24.3	27	4.8	2.0	51	55	246	1.81	45.9	0.135	3.4	13.4	SST	CG	N
1.225	31.12	72719	4.50	114.3	.929	23.6	45	7.9	2.4	61	108	480	2.11	53.6	0.148	3.8	14.3	MW	CG	N
1.225	31.12	72719S	4.50	114.3	.929	23.6	38	6.7	1.9	48	73	322	2.11	53.6	0.148	3.8	14.3	SST	CG	N
1.225	31.12	72727	4.50	114.3	.913	23.2	60	11	2.1	54	128	571	2.13	54.0	0.156	4.0	13.6	MW	CG	N
1.225	31.12	72727S	4.50	114.3	.913	23.2	51	8.9	1.6	41	81	362	2.13	54.0	0.156	4.0	13.6	SST	CG	N
1.225	31.12	72738	4.50	114.3	.901	22.9	69	12	2.1	53	143	637	2.27	57.6	0.162	4.1	14.0	MW	CG	N
1.225	31.12	72738S	4.50	114.3	.901	22.9	58	10	1.6	40	91	404	2.27	57.6	0.162	4.1	14.0	SST	CG	N
1.225	31.12	72749	4.50	114.3	.871	22.1	98	17	1.9	48	185	824	2.57	65.2	0.177	4.5	14.5	MW	CG	N
1.225	31.12	72749S	4.50	114.3	.871	22.1	83	15	1.4	36	118	523	2.57	65.2	0.177	4.5	14.5	SST	CG	N
1.225	31.12	72757	4.50	114.3	.841	21.4	140	24	1.6	41	226	1005	2.81	71.3	0.192	4.9	14.6	MW	CG	N
1.225	31.12	72757S	4.50	114.3	.841	21.4	119	21	1.2	29	138	613	2.81	71.3	0.192	4.9	14.6	SST	CG	N
1.225	31.12	72764	4.50	114.3	.811	20.6	196	34	1.4	36	281	1248	3.05	77.6	0.207	5.3	14.8	MW	CG	N
1.225	31.12	72764S	4.50	114.3	.811	20.6	167	29	1.0	26	171	761	3.05	77.6	0.207	5.3	14.8	SST	CG	N
1.225	31.12	72636	5.00	127.0	1.055	26.8	5.3	.93	4.0	102	21	95	.98	24.8	0.085	2.2	11.5	MW	CG	N
1.225	31.12	72636S	5.00	127.0	1.055	26.8	4.5	.79	3.6	92	16	72	.98	24.8	0.085	2.2	11.5	SST	CG	N
1.225	31.12	72650	5.00	127.0	1.033	26.2	8.5	1.5	3.8	98	33	145	1.15	29.3	0.096	2.4	12.0	MW	CG	N
1.225	31.12	72650S	5.00	127.0	1.033	26.2	7.2	1.3	3.1	78	22	99	1.15	29.3	0.096	2.4	12.0	SST	CG	N
1.225	31.12	72663	5.00	127.0	1.015	25.8	12	2.0	3.6	93	42	187	1.35	34.3	0.105	2.7	12.9	MW	CG	N
1.225	31.12	72663S	5.00	127.0	1.015	25.8	9.8	1.7	3.0	75	29	129	1.35	34.3	0.105	2.7	12.9	SST	CG	N
1.225	31.12	72678	5.00	127.0	1.001	25.4	16	2.9	3.1	79	51	227	1.36	34.5	0.112	2.8	12.1	MW	CG	N
1.225	31.12	72678S	5.00	127.0	1.001	25.4	14	2.4	2.4	61	33	148	1.36	34.5	0.112	2.8	12.1	SST	CG	N
1.225	31.12	72692	5.00	127.0	.975	24.8	21	3.7	3.2	81	68	301	1.81	46.0	0.125	3.2	14.5	MW	CG	N
1.225	31.12	72692S	5.00	127.0	.975	24.8	18	3.2	2.6	65	46	205	1.81	46.0	0.125	3.2	14.5	SST	CG	N
1.225	31.12	72707	5.00	127.0	.955	24.3	29	5.1	3.0	76	86	383	1.99	50.6	0.135	3.4	14.8	MW	CG	N
1.225	31.12	72707S	5.00	127.0	.955	24.3	25	4.3	2.3	57	55	246	1.99	50.6	0.135	3.4	14.8	SST	CG	N
1.225	31.12	72720	5.00	127.0	.929	23.6	40	7.1	2.7	68	108	478	2.33	59.2	0.148	3.8	15.8	MW		



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.234	31.34	II-92	.78	19.8	1.074	27.3	38	6.7	.38	9.5	14	64	.24	6.1	0.080	2.0	3.00	SPR	CG	N
1.234	31.34	3237	.84	21.4	1.082	27.5	31	5.4	.40	10	12	55	.23	5.8	0.076	1.9	3.00	SPR	CG	Z
1.234	31.34	3045	.88	22.2	1.110	28.2	7.0	1.2	.63	16	4.5	20	.24	6.1	0.062	1.6	4.00	SPR	CG	Z
1.234	31.34	1805	.88	22.2	1.080	27.4	33	5.7	.55	14	18	80	.23	5.9	0.077	2.0	3.00	MW	CG	Z
1.234	31.34	EE-77	.94	23.8	.954	24.2	281	49	.24	6.1	68	302	.49	12.4	0.140	3.6	3.50	SPR	CG	Z
1.234	31.34	12495	1.03	26.2	1.040	26.4	58	10	.42	11	24	109	.34	8.6	0.097	2.5	3.50	SPR	CG	Z
1.234	31.34	12094	1.19	30.2	.984	25.0	103	18	.49	12	50	223	.56	14.3	0.125	3.2	4.50	SPR	CG	Z
1.234	31.34	11597	1.31	33.3	.994	25.2	54	9.4	.47	12	25	113	.84	21.3	0.120	3.0	6.00	SPR	CG	Z
1.234	31.34	10120	1.38	34.9	1.100	27.9	3.7	.64	.91	23	3.3	15	.47	11.9	0.067	1.7	7.00	SPR	CG	Z
1.234	31.34	10499	1.41	35.7	1.040	26.4	58	10	.42	11	24									



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.250	31.75	33	4.00	101.6	.800	20.3	302	53	.79	20	239	1061	3.00	76.2	0.225	5.7	13.3	HD	CG	Z
1.250	31.75	4264	4.50	114.3	1.010	25.7	23	4.0	1.9	49	44	195	1.44	36.6	0.120	3.0	11.0	SPR	C	Z
1.250	31.75	3179	4.59	116.7	1.024	26.0	10	1.8	2.6	65	26	115	2.02	51.3	0.113	2.9	18.0	SPR	CG	Z
1.250	31.75	11681	4.63	117.5	.980	24.9	26	4.5	2.4	60	60	268	2.09	53.1	0.135	3.4	15.5	SPR	CG	Z
1.250	31.75	S-954	4.75	120.7	1.124	28.5	.74	.13	3.6	90	2.6	12	1.20	30.4	0.063	1.6	18.0	SST	C	N
1.250	31.75	1765	4.75	120.7	1.068	27.1	5.8	1.0	3.5	88	20	89	1.18	30.0	0.091	2.3	13.0	HD	CG	Z
1.250	31.75	4100	5.00	127.0	.814	20.7	328	57	.69	18	226	1007	2.40	60.9	0.218	5.5	11.0	SPR	CG	Z
1.250	31.75	3145	5.06	128.6	.896	22.8	143	25	.91	23	130	578	1.77	45.0	0.177	4.5	10.0	SPR	CG	Z
1.250	31.75	12772	5.75	146.1</																



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.296	32.92	11527	1.25	31.8	1.086	27.6	52	9.1	.57	15	30	131	.53	13.3	0.105	2.7	4.00	SPR	CG	Z
1.296	32.92	3655	1.50	38.1	1.114	28.3	20	3.6	.94	24	19	86	.43	11.0	0.091	2.3	4.75	SPR	CG	Z
1.296	32.92	10402	1.63	41.3	1.086	27.6	34	6.0	.86	22	30	131	.53	13.3	0.105	2.7	5.00	SPR	CG	Z
1.296	32.92	3409	1.63	41.3	1.080	27.4	39	6.8	.83	21	32	143	.54	13.7	0.108	2.7	5.00	SPR	CG	Z
1.296	32.92	3955	1.69	42.8	1.172	29.8	2.8	.49	1.3	32	3.5	16	.43	11.0	0.062	1.6	6.00	SPR	C	Z
1.296	32.92	2550	1.75	44.5	1.100	27.9	22	3.9	1.2	31	27	119	.54	13.7	0.098	2.5	5.50	MW	CG	Z
1.296	32.92	12015	1.75	44.5	1.086	27.6	34	6.0	.86	22	30	131	.53	13.3	0.105	2.7	5.00	SPR	CG	Z
1.296	32.92	10902	2.38	60.3	1.116	28.3	7.9	1.4	1.7	42	13	59	.72	18.3	0.090	2.3	8.00	SST	CG	N
1.296	32.92	11771	2.50	63.5	1.046	26.6	55	9.6	.88	22	48	213	.75	19.1	0.125	3.2	6.00	SPR	CG	Z
1.296	32.92	3151	2.56	6																




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.328	33.73	4306	8.25	209.6	.974	24.7	54	9.5	2.3	57	123	547	3.36	85.4	0.177	4.5	19.0	SPR	CG	Z
1.343	34.11	2634	.88	22.2	1.183	30.0	29	5.1	.45	12	13	59	.24	6.1	0.080	2.0	3.00	SPR	CG	Z
1.343	34.11	2774	1.50	38.1	1.191	30.3	5.9	1.0	1.0	27	6.2	27	.46	11.6	0.076	1.9	6.00	SPR	CG	Z
1.343	34.11	11807	1.50	38.1	1.181	30.0	12	2.2	1.1	28	14	61	.36	9.3	0.081	2.1	4.50	SPR	CG	Z
1.343	34.11	10639	1.72	43.6	.843	21.4	1229	215	.25	6.3	303	1348	1.38	34.9	0.250	6.4	5.50	SPR	CG	GI
1.343	34.11	2777	1.75	44.5	1.193	30.3	5.8	1.0	1.3	33	7.5	34	.44	11.2	0.075	1.9	6.00	MW	CG	Z
1.343	34.11	3061	1.88	47.6	1.155	29.3	18	3.1	1.2	29	21	91	.49	12.5	0.094	2.4	5.25	SPR	CG	Z
1.343	34.11	11643	1.88	47.6	1.151	29.2	25	4.4	.87	22	22	97	.43	11.0	0.096	2.4	4.50	SPR	CG	Z
1.343	34.11	1717	2.09	53.2	1.233	31														




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.375	34.93	S-1087	1.63	41.3	1.135	28.8	48	8.4	.77	19	37	163	.57	14.5	0.120	3.0	4.75	SST	CG	N
1.375	34.93	11628	1.63	41.3	1.123	28.5	41	7.2	.81	20	33	148	.82	20.8	0.126	3.2	6.50	SPR	CG	Z
1.375	34.93	S-326	1.69	42.8	1.105	28.1	63	11	.78	20	50	221	.74	18.9	0.135	3.4	5.50	SST	CG	N
1.375	34.93	3560	1.75	44.5	.991	25.2	393	69	.37	9.3	144	641	.96	24.4	0.192	4.9	5.00	SPR	CG	Z
1.375	34.93	10401	1.97	50.0	1.063	27.0	104	18	.79	20	82	366	1.01	25.8	0.156	4.0	6.50	SPR	CG	Z
1.375	34.93	12610	2.00	50.8	1.041	26.4	141	25	.71	18	100	447	1.09	27.6	0.167	4.2	6.50	SPR	CG	Z
1.375	34.93	10299	2.13	54.0	1.193	30.3	13	2.3	1.4	35	18	81	.50	12.7	0.091	2.3	5.50	SPR	CG	Z
1.375	34.93	11671	2.13	54.0	1.041	26.4	141	25	.71	18	100	447	1.09	27.6	0.167	4.2	6.50	SPR	CG	Z
1.375	34.93	12779	2.19	55.6	1.079	27.4	79	14	.92	23	72	321	1.00	25.4	0.148	3.8	6.75	HD	CG	Z
1.375	34.93	4400	2.22	56.4	1.179	29.9	15	2.6	1.5	39	23	101	.61	15.6	0.098	2.5	6.25	SPR	CG	Z
1.375	34.93	4343	2.25	57.2	1.193	30.3	10	1.8	1.7	42	17	76	.59	15.0	0.091	2.3	6.50	SPR	CG	Z
1.375	34.93	S-1388	2.31	58.7	1.191	30.3	6.8	1.2	1.6	39	11	47	.76	19.3	0.092	2.3	8.25	SST	CG	N
1.375	34.93	11839	2.34	59.5	1.187	30.1	7.6	1.3	1.6	40	12	53	.78	19.7	0.094	2.4	8.25	SST	CG	N
1.375	34.93	S-450	2.44	61.9	1.191	30.3	7.1	1.2	1.7	43	12	54	.74	18.7	0.092	2.3	8.00	SST	CG	N
1.375	34.93	10309	2.44	61.9	1.021	25.9	164	29	.73	18	119	530	1.24	31.5	0.177	4.5	7.00	SPR	CG	Z
1.375	34.93	10348	2.50	63.5	1.193	30.3	8.5	1.5	1.8	46	15	68	.68	17.3	0.091	2.3	7.50	SPR	CG	Z
1.375	34.93	12092	2.50	63.5	1.167	29.6	18	3.2	1.4	35	25	112	.73	18.5	0.104	2.6	6.00	SST	C	N
1.375	34.93	73	2.50	63.5	1.105	28.1	48	8.4	1.2	29	55	245	.98	24.9	0.135	3.4	7.25	HD	CG	Z
1.375	34.93	S-347	2.50	63.5	1.105	28.1	46	8.0	1.1	28	50	221	.91	23.1	0.135	3.4	6.75	SST	CG	N
1.375	34.93	12420	2.75	69.9	1.277	32.4	.89	.16	2.4	61	2.1	9.5	.34	8.7	0.049	1.2	6.00	SPR	C	Z
1.375	34.93	269	2.75	69.9	1.135	28.8	27	4.8	1.5	37	40	178	1.02	25.9	0.120	3.0	7.50	HD	C	Z
1.375	34.93	3464	2.75	69.9	1.105	28.1	31	5.5	1.3	32	40	176	1.49	37.7	0.135	3.4	10.0	HD	C	Z
1.375	34.93	54	2.75	69.9	1.021	25.9	122	21	.98	25	119	530	1.55	39.3	0.177	4.5	8.75	HD	CG	Z
1.375	34.93	10742	2.88	73.0	1.215	30.9	5.4	.95	2.3	59	13	56	.56	14.2	0.080	2.0	7.00	SPR	CG	Z
1.375	34.93	4355	2.94	74.6	1.205	30.6	4.0	.70	2.0	51	8.1	36	.91	23.2	0.085	2.2	10.8	SPR	CG	Z
1.375	34.93	S-1209	3.00	76.2	1.135	28.8	20	3.5	1.8	46	37	163	1.02	25.9	0.120	3.0	8.50	SST	CG	N
1.375	34.93	11266	3.00	76.2	1.021	25.9	153	27	.69	18	106	471	1.19	30.3	0.177	4.5	6.75	SST	CG	N
1.375	34.93	12048	3.47	88.1	1.125	28.6	28	4.8	1.6	42	45	201	1.06	27.0	0.125	3.2	8.50	SPR	CG	N
1.375	34.93	1557	3.50	88.9	1.259	32.0	.89	.16	2.9	73	2.5	11	.64	16.2	0.058	1.5	10.0	SPR	C	Z
1.375	34.93	S-289	3.75	95.3	1.251	31.8	1.5	.26	3.2	82	4.8	21	.53	13.4	0.062	1.6	7.50	SST	C	N
1.375	34.93	2591	3.75	95.3	1.231	31.3	1.6	.27	2.8	71	4.3	19	.95	24.2	0.072	1.8	13.3	HD	CG	Z
1.375	34.93	S-103	3.75	95.3	1.231	31.3	2.6	.46	3.1	79	8.2	37	.63	16.0	0.072	1.8	7.75	SST	C	N
1.375	34.93	S-1355	3.75	95.3	1.199	30.5	7.0	1.2	2.3	58	16	72	.62	15.6	0.088	2.2	7.00	SST	CG	N
1.375	34.93	S-445	3.75	95.3	1.175	29.8	6.0	1.1	2.6	65	15	68	1.20	30.5	0.100	2.5	12.0	SST	CG	N
1.375	34.93	898	3.75	95.3	1.105	28.1	29	5.2	1.9	48	55	245	1.55	39.4	0.135	3.4	10.5	HD	C	Z
1.375	34.93	S-195	3.75	95.3	1.063	27.0	63	11	1.2	30	73	325	1.33	33.7	0.156	4.0	8.50	SST	CG	N
1.375	34.93	S-327	3.88	98.4	1.231	31.3	2.6	.46	3.2	82	8.6	38	.63	16.0	0.072	1.8	7.75	SST	C	N
1.375	34.93	3987	4.00	101.6	1.021	25.9	80	14	1.5	38	119	530	2.17	55.1	0.177	4.5	12.3	SPR	CG	Z
1.375	34.93	861	4.13	104.8	1.105	28.1	27	4.7	2.1	52	55	245	1.53	38.9	0.135	3.4	11.3	HD	CG	Z
1.375	34.93	11513	4.38	111.1	1.217	30.9	3.7	.64	3.4	86	12	56	.79	20.1	0.079	2.0	9.00	SPR	CG	Z
1.375	34.93	823	4.38	111.1	1.079	27.4	36	6.3	2.0	51	72	321	1.83	46.4	0.148	3.8	12.3	HD	CG	Z
1.375	34.93	811	4.50	114.3	1.021	25.9	70	12	1.7	43	119	530	2.43	61.8	0.177	4.5	13.8	HD	CG	Z
1.375	34.93	10363	4.75	120.7	1.181	30.0	6.8	1.2	3.3	83	22	98	1.07	27.1	0.097	2.5	11.0	SPR	CG	Z
1.375	34.93	S-3002	5.38	136.5	1.221	31.0	3.3	.59	3.2	82	11	48	.69	17.6	0.077	2.0	8.00	SST	C	N
1.375	34.93	7005	5.38	136.5	1.001	25.4	75	13	1.8	45	134	594	3.30	83.8	0.187	4.7	16.3	HD	C	Z
1.375	34.93	389	6.00	152.4	1.135	28.8	13	2.2	3.2	81	40	178	1.68	42.7	0.120	3.0	14.0	HD	CG	Z
1.375	34.93	11977	6.50	165.1	.989	25.1	107	19	1.4	35	146	651	2.56	65.0	0.193	4.9	13.3	SPR	CG	Z
1.375	34.93	845	8.00	203.2	1.021	25.9	44	7.8	2.7	68	119	530	3.63	92.2	0.177	4.5	20.5	HD	CG	Z
1.375	34.93	383	9.75	247.7	1.215	30.9	1.1	.19	7.5	191	8.1	36	2.24	56.9	0.080	2.0	27.0	HD	C	Z
1.375	34.93	850	10.0	254.0	1.051	26.7	21	3.6	4.4	112	92	409	4.81	122.1	0.162	4.1	28.7	HD	C	Z
1.375	34.93	11489	10.9	277.8	1.019	25.9	32	5.6	3.8	97	121	539	5.25	133.4	0.178	4.5	28.5	HD	CG	Z
1.375	34.93	862	12.0	304.8	1.105	28.1	8.6	1.5	6.4	162	55	245	4.32	109.7	0.135	3.4	31.0	HD	C	Z
1.375	34.93	824	12.0	304.8	1.079	27.4	12	2.2	5.9	149	72	321	4.79	121.5	0.148	3.8	32.3	HD	CG	Z
1.375	34.93	841	12.0	304.8	.991	25.2	35	6.1	4.2	106	144	641	6.91	175.6	0.192	4.9	36.0	HD	CG	Z
1.375	34.93	803	12.0	304.8	.961	24.4	49	8.5	3.7	93	179	798	7.45	189.3	0.207	5.3	36.0	HD	CG	Z
1.375	34.93	801	12.0	304.8	.925	23.5	79	14	2.8	70	220	977</								




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	ENDS	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.400	35.56	72775	2.25	57.2	1.046	26.6	169	30	.97	25	164	730	1.17	29.8	0.177	4.5	6.63	MW	CG	N
1.400	35.56	72775S	2.25	57.2	1.046	26.6	143	25	.73	18	104	463	1.17	29.8	0.177	4.5	6.63	SST	CG	N
1.400	35.56	72767	2.50	63.5	1.076	27.3	103	18	1.2	31	127	563	1.15	29.3	0.162	4.1	7.13	MW	CG	N
1.400	35.56	72767S	2.50	63.5	1.076	27.3	87	15	.92	23	80	357	1.15	29.3	0.162	4.1	7.13	SST	CG	N
1.400	35.56	72776	2.50	63.5	1.046	26.6	149	26	1.1	28	164	730	1.26	32.0	0.177	4.5	7.13	MW	CG	N
1.400	35.56	72776S	2.50	63.5	1.046	26.6	127	22	.82	21	104	463	1.26	32.0	0.177	4.5	7.13	SST	CG	N
1.400	35.56	72768	3.00	76.2	1.076	27.3	84	15	1.5	39	127	563	1.34	33.9	0.162	4.1	8.25	MW	CG	N
1.400	35.56	72768S	3.00	76.2	1.076	27.3	71	12	1.1	29	80	357	1.34	33.9	0.162	4.1	8.25	SST	CG	N
1.400	35.56	72777	3.00	76.2	1.046	26.6	120	21	1.4	35	164	730	1.48	37.7	0.177	4.5	8.38	MW	CG	N
1.400	35.56	72777S	3.00	76.2	1.046	26.6	102	18	1.0	26	104	463	1.48	37.7	0.177	4.5	8.38	SST	CG	N
1.400	35.56	72769	3.50	88.9	1.076	27.3	70	12	1.8	46	127	563	1.52	38.6	0.162	4.1	9.38	MW	CG	N
1.400	35.56	72769S	3.50	88.9	1.076	27.3	60	10	1.3	34	80	357	1.52	38.6	0.162	4.1	9.38	SST	CG	N
1.400	35.56	72778	3.50	88.9	1.046	26.6	100	18	1.6	42	164	730	1.73	43.8	0.177	4.5	9.75	MW	CG	N
1.400	35.56	72778S	3.50	88.9	1.046	26.6	85	15	1.2	31	104	463	1.73	43.8	0.177	4.5	9.75	SST	CG	N
1.400	35.56	72770	4.00	101.6	1.076	27.3	61	11	2.1	53	127	563	1.72	43.7	0.162	4.1	10.6	MW	CG	N
1.400	35.56	72770S	4.00	101.6	1.076	27.3	52	9.0	1.6	39	80	357	1.72	43.7	0.162	4.1	10.6	SST	CG	N
1.400	35.56	72779	4.00	101.6	1.046	26.6	87	15	1.9	48	164	730	1.92	48.9	0.177	4.5	10.9	MW	CG	N
1.400	35.56	72779S	4.00	101.6	1.046	26.6	74	13	1.4	36	104	463	1.92	48.9	0.177	4.5	10.9	SST	CG	N
1.400	35.56	72771	4.25	108.0	1.076	27.3	57	10	2.2	57	127	563	1.80	45.8	0.162	4.1	11.1	MW	CG	N
1.400	35.56	72771S	4.25	108.0	1.076	27.3	48	8.5	1.7	42	80	357	1.80	45.8	0.162	4.1	11.1	SST	CG	N
1.400	35.56	72780	4.25	108.0	1.046	26.6	81	14	2.0	51	164	730	2.04	51.7	0.177	4.5	11.5	MW	CG	N
1.400	35.56	72780S	4.25	108.0	1.046	26.6	69	12	1.5	38	104	463	2.04	51.7	0.177	4.5	11.5	SST	CG	N
1.400	35.56	72772	4.50	114.3	1.076	27.3	54	9.4	2.4	60	127	563	1.90	48.3	0.162	4.1	11.8	MW	CG	N
1.400	35.56	72772S	4.50	114.3	1.076	27.3	45	8.0	1.8	45	80	357	1.90	48.3	0.162	4.1	11.8	SST	CG	N
1.400	35.56	72781	4.50	114.3	1.046	26.6	76	13	2.2	55	164	730	2.15	54.5	0.177	4.5	12.1	MW	CG	N
1.400	35.56	72781S	4.50	114.3	1.046	26.6	65	11	1.6	41	104	463	2.15	54.5	0.177	4.5	12.1	SST	CG	N
1.400	35.56	72773	5.00	127.0	1.076	27.3	48	8.4	2.7	67	127	563	2.09	53.0	0.162	4.1	12.9	MW	CG	N
1.400	35.56	72773S	5.00	127.0	1.076	27.3	41	7.1	2.0	50	80	357	2.09	53.0	0.162	4.1	12.9	SST	CG	N
1.400	35.56	72782	5.00	127.0	1.046	26.6	69	12	2.4	60	164	730	2.32	59.0	0.177	4.5	13.1	MW	CG	N
1.400	35.56	72782S	5.00	127.0	1.046	26.6	59	10	1.8	45	104	463	2.32	59.0	0.177	4.5	13.1	SST	CG	N
1.400	35.56	72774	5.25	133.4	1.076	27.3	45	7.9	2.8	71	127	563	2.19	55.5	0.162	4.1	13.5	MW	CG	N
1.400	35.56	72774S	5.25	133.4	1.076	27.3	39	6.8	2.1	53	80	357	2.19	55.5	0.162	4.1	13.5	SST	CG	N
1.400	35.56	72783	5.25	133.4	1.046	26.6	65	11	2.5	64	164	730	2.46	62.4	0.177	4.5	13.9	MW	CG	N
1.400	35.56	72783S	5.25	133.4	1.046	26.6	55	9.7	1.9	48	104	463	2.46	62.4	0.177	4.5	13.9	SST	CG	N
1.406	35.71	S-1241	.75	19.1	1.136	28.9	202	35	.24	6.1	49	216	.41	10.3	0.135	3.4	3.00	SST	CG	N
1.406	35.71	S-70	.88	22.2	1.246	31.6	15	2.6	.60	15	8.7	39	.28	7.1	0.080	2.0	3.50	SST	CG	N
1.406	35.71	S-3246	1.00	25.4	1.322	33.6	.78	.14	.83	21	.65	2.9	.17	4.3	0.042	1.1	4.00	SST	CG	N
1.406	35.71	S-3024	1.00	25.4	1.256	31.9	9.6	1.7	.64	16	6.2	27	.36	9.0	0.075	1.9	3.75	SST	C	N
1.406	35.71	S-3018	1.13	28.6	1.226	31.1	18	3.2	.68	17	12	54	.45	11.4	0.090	2.3	4.00	SST	C	N
1.406	35.71	S-3075	1.13	28.6	1.032	26.2	563	99	.20	5.1	113	501	.65	16.6	0.187	4.7	3.50	SST	CG	N
1.406	35.71	NN-77	1.22	31.0	1.086	27.6	288	50	.27	6.8	77	343	.56	14.2	0.160	4.1	3.50	SST	CG	N
1.406	35.71	3017	1.25	31.8	1.282	32.6	2.5	.44	.85	22	2.1	9.4	.40	10.2	0.062	1.6	5.50	SPR	C	Z
1.406	35.71	11980	1.25	31.8	1.082	27.5	343	60	.26	6.7	90	401	.57	14.4	0.162	4.1	3.50	SPR	CG	Z
1.406	35.71	3324	1.28	32.5	1.166	29.6	47	8.2	.68	17	32	142	.60	15.2	0.120	3.0	5.00	HD	CG	Z
1.406	35.71	12192	1.34	34.1	1.296	32.9	2.1	.37	1.0	26	2.2	9.9	.30	7.7	0.055	1.4	4.50	SPR	C	Z
1.406	35.71	11908	1.50	38.1	1.300	33.0	1.6	.28	1.2	31	2.0	8.7	.29	7.4	0.053	1.3	4.50	SST	C	N
1.406	35.71	12009	1.50	38.1	1.296	32.9	.82	.14	1.0	26	.85	3.8	.47	11.9	0.055	1.4	8.50	SPR	CG	GI
1.406	35.71	S-333	1.50	38.1	1.136	28.9	67	12	.72	18	49	216	.68	17.1	0.135	3.4	5.00	SST	CG	N
1.406	35.71	S-1676	1.63	41.3	1.240	31.5	13	2.3	1.0	26	13	59	.42	10.5	0.083	2.1	4.00	SST	C	N
1.406	35.71	281	1.75	44.5	1.110	28.2	104	18	.68	17	71	315	.79	20.0	0.148	3.8	5.33	HD	CG	Z
1.406	35.71	11424	1.91	48.4	1.032	26.2	216	38	.61	15	131	582	1.22	30.9	0.187	4.7	6.50	SPR	CG	N
1.406	35.71	11283	2.13	54.0	1.224	31.1	8.7	1.5	1.5	38	13	57	.64	16.2	0.091	2.3	7.00	HD	CG	Z
1.406	35.71	10547	2.13	54.0	1.034	26.3	199	35	.65	16	129	573	1.26	31.9	0.186	4.7	6.75	SPR	CG	Z
1.406	35.71	S-1250	2.50	63.5	1.136	28.9	43	7.5	1.1	29	49	216	.91	23.1	0.135	3.4	6.75	SST	CG	N
1.406	35.71	12058	3.16	80.2	.992	25.2	236	41	.75	19	176	782	1.76	44.7	0.207	5.3	8.50	SPR	CG	Z
1.406	35.71	1683	3.25	82.6	.984	25.0	257	45	.72	18	186									



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.421	36.09	4194	4.00	101.6	1.281	32.5	1.3	.22	3.0	77	3.8	17	.98	24.9	0.070	1.8	13.0	SPR	C	Z
1.421	36.09	3141	5.13	130.2	1.261	32.0	2.6	.45	4.1	105	11	47	1.00	25.4	0.080	2.0	11.5	SPR	C	Z
1.421	36.09	12460	12.0	304.8	1.003	25.5	55	9.5	3.3	83	179	796	6.32	160.6	0.209	5.3	30.3	SPR	CG	N
1.421	36.09	4018	27.5	698.5	.921	23.4	60	11	4.8	122	289	1285	15.0	381.0	0.250	6.4	60.0	SPR	CG	N
1.437	36.50	S-1550	.56	14.3	1.237	31.4	70	12	.29	7.3	20	89	.28	7.0	0.100	2.5	2.75	SST	CG	N
1.437	36.50	DD-88	.69	17.4	1.217	30.9	45	7.9	.25	6.3	11	49	.44	11.2	0.110	2.8	4.00	SPR	CG	Z
1.437	36.50	S-3059	.88	22.2	1.281	32.5	12	2.2	.52	13	6.4	29	.35	8.9	0.078	2.0	3.50	SST	C	N
1.437	36.50	12222	1.00	25.4	1.293	32.8	15	2.7	.60	15	9.1	40	.22	5.5	0.072	1.8	3.00	SPR	CG	Z
1.437	36.50	S-151	1.50	38.1	1.347	34.2	.32	.06	1.1	28	.35	1.5	.41	10.3	0.045	1.1	8.00	SST	C	N
1.437	36.50	S-1033	1.50	38.1	1.277	32.4	5.9	1.0	.98	25	5.7	26	.52	13.2	0.080	2.0	5.50	SST	C	N
1.437	36.50	11360	1.50	38.1	1.255	31.9	12	2.1	1.0	27	12	56	.46	11.6	0.091	2.3	5.00	SST	CG	N
1.437	36.50	3071	1.50	38.1	1.173	29.8	56	9.8	.77	20	43	193	.73	18.4	0.132	3.4	5.50	SPR	CG	Z
1.437	36.50	S-944	1.69	42.8	1.237	31.4	26	4.6	.82	21	21	95	.40	10.2	0.100	2.5	4.00	SST	CG	N
1.437	36.50	12487	1.75	44.5	1.317	33.5	1.0	.18	1.2	31	1.3	5.6	.54	13.7	0.060	1.5	8.00	SST	C	N
1.437	36.50	B17-167	1.84	46.8	1.125	28.6	135	24	.58	15	79	351	.78	19.8	0.156	4.0	5.00	SPR	CG	N
1.437	36.50	11531	2.72	69.0	1.013	25.7	234	41	.65	17	152	678	2.07	52.5	0.212	5.4	8.75	SPR	CG	Z
1.437	36.50	3909	2.75	69.9	1.317	33.5	1.8	.31	2.3	59	4.2	18	.42	10.7	0.060	1.5	6.00	SPR	C	Z
1.437	36.50	3288	2.75	69.9	1.017	25.8	275	48	.65	17	180	799	1.58	40.0	0.210	5.3	7.50	SPR	CG	Z
1.437	36.50	12069	2.88	73.0	1.287	32.7	3.0	.53	2.3	58	6.8	30	.60	15.2	0.075	1.9	8.00	SPR	CG	Z
1.437	36.50	3704	3.00	76.2	1.327	33.7	1.2	.22	2.7	68	3.3	15	.33	8.4	0.055	1.4	6.00	SPR	CG	Z
1.437	36.50	2753	3.13	79.4	1.287	32.7	3.0	.53	2.5	64	7.6	34	.60	15.2	0.075	1.9	8.00	HD	CG	Z
1.437	36.50	10719	3.31	84.1	1.335	33.9	.52	.09	2.9	72	1.5	6.6	.46	11.7	0.051	1.3	9.00	SPR	CG	Z
1.437	36.50	3407	3.38	85.7	1.177	29.9	31	5.4	1.5	39	47	210	1.04	26.4	0.130	3.3	8.00	SPR	CG	Z
1.437	36.50	S-303	3.59	91.3	1.277	32.4	2.6	.46	2.8	71	7.3	32	.80	20.3	0.080	2.0	10.0	SST	CG	N
1.437	36.50	10594	3.75	95.3	1.265	32.1	3.2	.56	2.7	69	8.7	39	1.03	26.2	0.086	2.2	12.0	SPR	CG	Z
1.437	36.50	10823	4.00	101.6	1.167	29.6	30	5.2	1.8	45	53	235	1.38	35.1	0.135	3.4	9.25	SPR	C	Z
1.437	36.50	S-369	4.88	123.8	1.137	28.9	37	6.5	1.7	43	63	278	1.50	38.1	0.150	3.8	10.0	SST	CG	N
1.437	36.50	7007	5.63	142.9	1.023	26.0	100	18	1.7	44	172	767	3.60	91.4	0.207	5.3	16.3	HD	C	Z
1.437	36.50	3049	6.88	174.6	1.077	27.4	47	8.3	2.4	62	115	510	3.26	82.9	0.180	4.6	18.0	SPR	CG	Z
1.437	36.50	10454	8.88	225.4	1.187	30.1	13	2.2	3.5	88	43	193	2.02	51.2	0.125	3.2	15.8	SPR	CG	Z
1.437	36.50	4236	14.5	368.3	1.083	27.5	20	3.6	5.6	142	114	509	6.64	168.6	0.177	4.5	36.5	SPR	C	Z
1.437	36.50	4040	20.5	520.7	1.113	28.3	12	2.1	7.4	188	88	392	6.40	162.6	0.162	4.1	40.0	SPR	CG	Z
1.437	36.50	4029	23.0	584.2	1.113	28.3	12	2.1	7.2	183	88	392	6.64	168.7	0.162	4.1	41.0	SPR	CG	Z
1.453	36.91	3299	1.53	38.9	1.227	31.2	49	8.5	.65	17	32	142	.45	11.5	0.113	2.9	4.00	SPR	CG	Z
1.453	36.91	3297	1.75	44.5	1.243	31.6	12	2.1	.91	23	11	48	.84	21.3	0.105	2.7	8.00	HD	CG	Z
1.453	36.91	12297	1.94	49.2	1.323	33.6	3.2	.56	1.6	41	5.2	23	.33	8.3	0.065	1.7	5.00	SPR	CG	Z
1.453	36.91	10339	2.06	52.4	1.233	31.3	35	6.1	.85	21	29	131	.50	12.6	0.110	2.8	4.50	SPR	CG	Z
1.453	36.91	4359	2.06	52.4	1.069	27.2	216	38	.63	16	137	610	1.25	31.7	0.192	4.9	6.50	SPR	CG	Z
1.453	36.91	11791	2.41	61.1	1.203	30.6	37	6.6	1.1	29	43	191	.75	19.1	0.125	3.2	6.00	SPR	CG	Z
1.453	36.91	12616	2.50	63.5	1.203	30.6	37	6.6	1.6	41	60	267	.88	22.2	0.125	3.2	6.00	MW	C	N
1.453	36.91	B11-63	2.84	72.2	1.157	29.4	62	11	1.1	28	69	305	1.04	26.3	0.148	3.8	7.00	SPR	CG	N
1.453	36.91	B17-203	2.88	73.0	1.275	32.4	6.3	1.1	2.3	57	14	63	.62	15.8	0.089	2.3	7.00	SST	CG	N
1.453	36.91	11238	3.00	76.2	1.141	29.0	58	10	1.4	34	78	348	1.37	34.7	0.156	4.0	8.75	SPR	CG	Z
1.453	36.91	12177	3.03	77.0	1.269	32.2	7.8	1.4	2.3	58	18	80	.67	16.9	0.092	2.3	7.25	SPR	CG	GI
1.453	36.91	4026	20.3	514.4	1.123	28.5	12	2.1	7.8	197	92	410	7.26	184.4	0.165	4.2	44.0	SPR	CG	Z
1.453	36.91	4038	21.0	533.4	1.099	27.9	16	2.9	6.9	176	113	503	7.70	195.6	0.177	4.5	43.5	SPR	CG	Z
1.453	36.91	4032	22.5	571.5	1.093	27.8	16	2.7	7.3	185	114	505	8.82	224.0	0.180	4.6	49.0	SPR	CG	Z
1.460	37.08	72784	1.50	38.1	1.236	31.4	41	7.2	1.0	26	42	188	.48	12.1	0.112	2.8	4.25	MW	CG	N
1.460	37.08	72784S	1.50	38.1	1.236	31.4	35	6.1	.80	20	28	125	.48	12.1	0.112	2.8	4.25	SST	CG	N
1.460	37.08	72794	1.50	38.1	1.210	30.7	61	11	.95	24	58	257	.55	13.9	0.125	3.2	4.38	MW	CG	N
1.460	37.08	72794S	1.50	38.1	1.210	30.7	52	9.0	.76	19	39	173	.55	13.9	0.125	3.2	4.38	SST	CG	N
1.460	37.08	72800	1.50	38.1	1.190	30.2	80	14	.89	23	72	319	.61	15.4	0.135	3.4	4.50	MW	CG	N
1.460	37.08	72800S	1.50	38.1	1.190	30.2	68	12	.69	17	47	209	.61	15.4	0.135	3.4	4.50	SST	CG	N
1.460	37.08	72810	1.50	38.1	1.164	29.6	114	20	.82	21	93	412	.68	17.4	0.148	3.8	4.63	MW	CG	N
1.460	37.08	72810S	1.50	38.1	1.164	29.6	97	17	.64	16	62	274	.68	17.4	0.148	3.8	4.63	SST	CG	N
1.460	37.08	72817	1.50	38.1	1.148	29.2	143	25	.76	19	109	485	.72	18.3	0.156					




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./in.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.460	37.08	72802S	2.50	63.5	1.190	30.2	38	6.6	1.2	32	47	209	.89	22.7	0.135	3.4	6.63	SST	CG	N
1.460	37.08	72812	2.50	63.5	1.164	29.6	62	11	1.5	38	92	409	1.02	25.8	0.148	3.8	6.88	MW	CG	N
1.460	37.08	72812S	2.50	63.5	1.164	29.6	53	9.2	1.2	30	62	274	1.02	25.8	0.148	3.8	6.88	SST	CG	N
1.460	37.08	72821	2.50	63.5	1.148	29.2	78	14	1.4	36	109	485	1.07	27.2	0.156	4.0	6.88	MW	CG	N
1.460	37.08	72821S	2.50	63.5	1.148	29.2	66	12	1.0	27	69	307	1.07	27.2	0.156	4.0	6.88	SST	CG	N
1.460	37.08	72834	2.50	63.5	1.136	28.9	88	15	1.3	34	118	526	1.15	29.3	0.162	4.1	7.13	MW	CG	N
1.460	37.08	72834S	2.50	63.5	1.136	28.9	75	13	1.0	26	77	343	1.15	29.3	0.162	4.1	7.13	SST	CG	N
1.460	37.08	72845	2.50	63.5	1.106	28.1	128	22	1.2	31	156	693	1.28	32.6	0.177	4.5	7.25	MW	CG	N
1.460	37.08	72845S	2.50	63.5	1.106	28.1	109	19	.92	23	100	445	1.28	32.6	0.177	4.5	7.25	SST	CG	N
1.460	37.08	72856	2.50	63.5	1.086	27.6	168	29	1.1	27	179	795	1.33	33.8	0.187	4.7	7.13	MW	CG	N
1.460	37.08	72856S	2.50	63.5	1.086	27.6	143	25	.76	19	109	484	1.33	33.8	0.187	4.7	7.13	SST	CG	N
1.460	37.08	72787	3.00	76.2	1.236	31.4	19	3.3	2.2	57	42	188	.77	19.6	0.112	2.8	6.88	MW	CG	N
1.460	37.08	72787S	3.00	76.2	1.236	31.4	16	2.8	1.7	44	28	125	.77	19.6	0.112	2.8	6.88	SST	CG	N
1.460	37.08	72797	3.00	76.2	1.210	30.7	28	4.8	2.1	53	57	255	.92	23.4	0.125	3.2	7.38	MW	CG	N
1.460	37.08	72797S	3.00	76.2	1.210	30.7	23	4.1	1.7	42	39	173	.92	23.4	0.125	3.2	7.38	SST	CG	N
1.460	37.08	72803	3.00	76.2	1.190	30.2	36	6.3	2.0	50	71	317	1.03	26.1	0.135	3.4	7.63	MW	CG	N
1.460	37.08	72803S	3.00	76.2	1.190	30.2	31	5.4	1.5	39	47	209	1.03	26.1	0.135	3.4	7.63	SST	CG	N
1.460	37.08	72813	3.00	76.2	1.164	29.6	51	8.9	1.8	46	92	409	1.18	30.1	0.148	3.8	8.00	MW	CG	N
1.460	37.08	72813S	3.00	76.2	1.164	29.6	43	7.5	1.4	36	62	274	1.18	30.1	0.148	3.8	8.00	SST	CG	N
1.460	37.08	72823	3.00	76.2	1.148	29.2	63	11	1.7	44	109	485	1.25	31.7	0.156	4.0	8.00	MW	CG	N
1.460	37.08	72823S	3.00	76.2	1.148	29.2	54	9.4	1.3	33	69	307	1.25	31.7	0.156	4.0	8.00	SST	CG	N
1.460	37.08	72835	3.00	76.2	1.136	28.9	71	13	1.6	42	117	522	1.36	34.5	0.162	4.1	8.38	MW	CG	N
1.460	37.08	72835S	3.00	76.2	1.136	28.9	61	11	1.3	32	77	343	1.36	34.5	0.162	4.1	8.38	SST	CG	N
1.460	37.08	72847	3.00	76.2	1.106	28.1	104	18	1.5	39	158	701	1.48	37.7	0.177	4.5	8.38	MW	CG	N
1.460	37.08	72847S	3.00	76.2	1.106	28.1	88	15	1.1	29	100	445	1.48	37.7	0.177	4.5	8.38	SST	CG	N
1.460	37.08	72857	3.00	76.2	1.086	27.6	138	24	1.3	33	179	795	1.52	38.6	0.187	4.7	8.13	MW	CG	N
1.460	37.08	72857S	3.00	76.2	1.086	27.6	117	21	.93	24	109	484	1.52	38.6	0.187	4.7	8.13	SST	CG	N
1.460	37.08	72788	3.50	88.9	1.236	31.4	16	2.8	2.6	67	42	188	.87	22.0	0.112	2.8	7.75	MW	CG	N
1.460	37.08	72788S	3.50	88.9	1.236	31.4	14	2.4	2.1	52	28	125	.87	22.0	0.112	2.8	7.75	SST	CG	N
1.460	37.08	72798	3.50	88.9	1.210	30.7	23	4.1	2.5	62	57	254	1.05	26.6	0.125	3.2	8.38	MW	CG	N
1.460	37.08	72798S	3.50	88.9	1.210	30.7	20	3.5	2.0	50	39	173	1.05	26.6	0.125	3.2	8.38	SST	CG	N
1.460	37.08	72804	3.50	88.9	1.190	30.2	31	5.4	2.3	59	71	316	1.18	30.0	0.135	3.4	8.75	MW	CG	N
1.460	37.08	72804S	3.50	88.9	1.190	30.2	26	4.6	1.8	46	47	209	1.18	30.0	0.135	3.4	8.75	SST	CG	N
1.460	37.08	72814	3.50	88.9	1.164	29.6	43	7.5	2.1	55	92	408	1.35	34.3	0.148	3.8	9.13	MW	CG	N
1.460	37.08	72814S	3.50	88.9	1.164	29.6	36	6.4	1.7	43	62	274	1.35	34.3	0.148	3.8	9.13	SST	CG	N
1.460	37.08	72825	3.50	88.9	1.148	29.2	53	9.4	2.0	52	109	485	1.44	36.7	0.156	4.0	9.25	MW	CG	N
1.460	37.08	72825S	3.50	88.9	1.148	29.2	45	7.9	1.5	39	69	307	1.44	36.7	0.156	4.0	9.25	SST	CG	N
1.460	37.08	72836	3.50	88.9	1.136	28.9	60	11	2.0	50	118	524	1.54	39.1	0.162	4.1	9.50	MW	CG	N
1.460	37.08	72836S	3.50	88.9	1.136	28.9	51	8.9	1.5	38	77	343	1.54	39.1	0.162	4.1	9.50	SST	CG	N
1.460	37.08	72849	3.50	88.9	1.106	28.1	87	15	1.8	46	157	698	1.70	43.3	0.177	4.5	9.63	MW	CG	N
1.460	37.08	72849S	3.50	88.9	1.106	28.1	74	13	1.3	34	100	445	1.70	43.3	0.177	4.5	9.63	SST	CG	N
1.460	37.08	72858	3.50	88.9	1.086	27.6	116	20	1.5	39	179	795	1.75	44.5	0.187	4.7	9.38	MW	CG	N
1.460	37.08	72858S	3.50	88.9	1.086	27.6	99	17	1.1	28	109	484	1.75	44.5	0.187	4.7	9.38	SST	CG	N
1.460	37.08	72789	4.00	101.6	1.236	31.4	14	2.4	3.0	77	42	188	.97	24.5	0.112	2.8	8.63	MW	CG	N
1.460	37.08	72789S	4.00	101.6	1.236	31.4	12	2.1	2.4	61	28	125	.97	24.5	0.112	2.8	8.63	SST	CG	N
1.460	37.08	72799	4.00	101.6	1.210	30.7	20	3.5	2.8	72	57	256	1.16	29.4	0.125	3.2	9.25	MW	CG	N
1.460	37.08	72799S	4.00	101.6	1.210	30.7	17	3.0	2.3	58	39	173	1.16	29.4	0.125	3.2	9.25	SST	CG	N
1.460	37.08	72805	4.00	101.6	1.190	30.2	27	4.6	2.7	68	71	316	1.32	33.4	0.135	3.4	9.75	MW	CG	N
1.460	37.08	72805S	4.00	101.6	1.190	30.2	23	3.9	2.1	53	47	209	1.32	33.4	0.135	3.4	9.75	SST	CG	N
1.460	37.08	72815	4.00	101.6	1.164	29.6	37	6.5	2.5	63	92	409	1.52	38.5	0.148	3.8	10.3	MW	CG	N
1.460	37.08	72815S	4.00	101.6	1.164	29.6	31	5.5	2.0	50	62	274	1.52	38.5	0.148	3.8	10.3	SST	CG	N
1.460	37.08	72827	4.00	101.6	1.148	29.2	46	8.1	2.4	60	109	485	1.60	40.6	0.156	4.0	10.3	MW	CG	N
1.460	37.08	72827S	4.00	101.6	1.148	29.2	39	6.9	1.8	45	69	307	1.60	40.6	0.156	4.0	10.3	SST	CG	N
1.460	37.08	72837	4.00	101.6	1.136	28.9	52	9.1	2.3	57	117	522	1.74	44.2	0.162	4.1	10.8	MW	CG	N
1.460	37.08	72837S	4.00	101.6	1.136	28.9	44	7.7	1.7	44	77	343	1.74	44.2	0.162	4.1	10.8	SST	CG	N
1.460	37.08	72851	4.00	101.6	1.106	28.1	75	13	2.1	53										



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.460	37.08	72839S	5.00	127.0	1.136	28.9	35	6.1	2.2	57	77	343	2.13	54.0	0.162	4.1	13.1	SST	CG	N
1.460	37.08	72855	5.00	127.0	1.106	28.1	59	10	2.7	67	157	698	2.35	59.6	0.177	4.5	13.3	MW	CG	N
1.460	37.08	72855S	5.00	127.0	1.106	28.1	50	8.8	2.0	51	100	445	2.35	59.6	0.177	4.5	13.3	SST	CG	N
1.460	37.08	72862	5.00	127.0	1.086	27.6	77	13	2.3	59	179	795	2.45	62.3	0.187	4.7	13.1	MW	CG	N
1.460	37.08	72862S	5.00	127.0	1.086	27.6	65	11	1.7	42	109	484	2.45	62.3	0.187	4.7	13.1	SST	CG	N
1.460	37.08	72863	5.25	133.4	1.086	27.6	73	13	2.4	62	179	795	2.55	64.7	0.187	4.7	13.6	MW	CG	N
1.460	37.08	72863S	5.25	133.4	1.086	27.6	62	11	1.8	45	109	484	2.55	64.7	0.187	4.7	13.6	SST	CG	N
1.468	37.29	S-3052	.69	17.4	1.410	35.8		.30 .05	.57	15		.17 .75	.12	2.9	0.029	0.7	3.00	SST	C	N
1.468	37.29	1853	1.00	25.4	1.198	30.4	134	24	.39	9.8	52	231	.47	12.0	0.135	3.4	3.50	SPR	CG	Z
1.468	37.29	3496	1.31	33.3	1.258	32.0	28	4.8	.84	21	23	103	.47	12.0	0.105	2.7	4.50	SPR	CG	Z
1.468	37.29	3456	1.31	33.3	1.018	25.9	959	168	.22	5.5	207	922	.90	22.9	0.225	5.7	4.00	SPR	CG	Z
1.468	37.29	11426	1.50	38.1	1.054	26.8	389	68	.37	9.5	146	648	1.04	26.3	0.207	5.3	5.00	SST	CG	N
1.468	37.29	S-1669	1.56	39.7	1.308	33.2	13	2.3	.88	22	11	51	.28	7.1	0.080	2.0	3.50	SST	CG	N
1.468	37.29	S-1358	1.75	44.5	1.268	32.2	24	4.3	.86	22	21	93	.40	10.2	0.100	2.5	4.00	SST	CG	N
1.468	37.29	S-1443	1.84	46.8	1.054	26.8	327	57	.45	11	146	648	1.14	28.9	0.207	5.3	5.50	SST	CG	N
1.468	37.29	S-3192	2.00	50.8	1.272	32.3	18	3.2	1.1	27	20	88	.44	11.2	0.098	2.5	4.50	SST	CG	N
1.468	37.29	S-1632	2.06	52.4	1.094	27.8	212	37	.51	13	108	482	1.03	26.1	0.187	4.7	5.50	SST	CG	N
1.468	37.29	11881	2.13	54.0	1.230	31.2	39	6.9	.94	24	37	163	.60	15.1	0.119	3.0	5.00	SPR	CG	N
1.468	37.29	S-987	2.13	54.0	1.226	31.1	35	6.2	1.0	25	35	157	.60	15.2	0.121	3.1	5.00	SST	CG	N
1.468	37.29	10336	2.19	55.6	.718	18.2	7917	1386	.10	2.6	799	3554	1.78	45.2	0.375	9.5	4.75	SPR	CG	Z
1.468	37.29	10368	2.25	57.2	1.084	27.5	235	41	.58	15	136	604	1.15	29.3	0.192	4.9	6.00	SPR	CG	Z
1.468	37.29	10317	2.38	60.3	1.068	27.1	215	38	.71	18	153	680	1.45	36.8	0.200	5.1	7.25	SPR	CG	Z
1.468	37.29	1743	2.41	61.1	1.304	33.1	4.9	.85	1.8	44	8.5	38	.66	16.7	0.082	2.1	7.00	HD	C	Z
1.468	37.29	S-1595	2.44	61.9	1.258	32.0	7.9	1.4	1.3	33	10	46	1.13	28.7	0.105	2.7	9.75	SST	CG	N
1.468	37.29	10048	2.44	61.9	1.054	26.8	251	44	.67	17	169	752	1.50	38.1	0.207	5.3	7.25	SPR	CG	Z
1.468	37.29	S-3057	2.50	63.5	1.284	32.6	11	2.0	1.4	36	16	73	.55	14.0	0.092	2.3	5.00	SST	C	N
1.468	37.29	10204	2.50	63.5	1.084	27.5	235	41	.58	15	136	604	1.15	29.3	0.192	4.9	6.00	SPR	CG	Z
1.468	37.29	10371	2.53	64.3	1.068	27.1	215	38	.71	18	153	680	1.45	36.8	0.200	5.1	7.25	SPR	CG	Z
1.468	37.29	S-3165	2.69	68.2	1.258	32.0	12	2.1	2.0	50	23	104	.74	18.7	0.105	2.7	7.00	SST	CG	N
1.468	37.29	11496	2.75	69.9	1.048	26.6	234	41	.75	19	176	784	1.89	48.0	0.210	5.3	8.00	SPR	CG	Z
1.468	37.29	S-3222	3.00	76.2	1.172	29.8	53	9.3	1.2	29	61	272	1.04	26.3	0.148	3.8	7.00	SST	CG	N
1.468	37.29	B17-200	3.28	83.3	1.232	31.3	17	2.9	2.0	50	33	145	.94	24.0	0.118	3.0	8.00	SST	CG	N
1.468	37.29	S-1598	3.50	88.9	1.310	33.3	2.3	.41	2.6	67	6.1	27	.87	22.1	0.079	2.0	10.0	SST	CG	N
1.468	37.29	S-3066	3.63	92.1	1.298	33.0	5.5	.96	2.5	63	14	61	.55	14.0	0.085	2.2	6.50	SST	CG	N
1.468	37.29	S-3184	4.50	114.3	1.268	32.2	7.5	1.3	2.8	71	21	93	.85	21.6	0.100	2.5	8.50	SST	CG	N
1.468	37.29	12270	4.59	116.7	1.298	33.0	3.5	.62	3.7	95	13	59	.85	21.6	0.085	2.2	10.0	SPR	CG	Z
1.468	37.29	12440	4.81	122.2	1.032	26.2	148	26	1.3	34	196	874	2.89	73.4	0.218	5.5	13.3	SPR	CG	Z
1.468	37.29	S-970	5.13	130.2	1.240	31.5	8.8	1.5	3.4	85	30	131	1.33	33.8	0.114	2.9	11.7	SST	CG	N
1.468	37.29	S-3216	5.25	133.4	1.310	33.3	1.6	.28	4.2	106	6.7	30	1.07	27.1	0.079	2.0	13.5	SST	CG	N
1.468	37.29	10388	5.75	146.1	1.030	26.2	148	26	1.3	34	199	886	2.96	75.1	0.219	5.6	13.5	SPR	CG	Z
1.468	37.29	11172	6.00	152.4	1.028	26.1	161	28	1.2	31	194	864	3.03	76.8	0.220	5.6	12.8	SPR	C	Z
1.484	37.69	S-1603	1.53	38.9	1.072	27.2	367	64	.30	7.5	108	481	1.24	31.4	0.206	5.2	5.00	SST	CG	N
1.484	37.69	S-383	3.25	82.6	1.274	32.4	13	2.3	1.9	47	24	107	.68	17.3	0.105	2.7	6.50	SST	CG	N
1.484	37.69	3023	3.38	85.7	1.172	29.8	61	11	1.3	32	77	341	1.25	31.7	0.156	4.0	8.00	SPR	CG	Z
1.484	37.69	S-1655	3.75	95.3	1.070	27.2	125	22	1.2	29	144	641	2.28	57.8	0.207	5.3	11.0	SST	CG	N
1.484	37.69	12412	5.00	127.0	1.380	35.1		.80 .14	4.4	112	3.5	16	.39	9.9	0.052	1.3	6.50	SPR	C	Z
1.484	37.69	1735	9.00	228.6	1.160	29.5	20	3.6	4.2	107	86	381	3.73	94.6	0.162	4.1	23.0	SPR	CG	Z
1.500	38.10	11898	.84	21.4	1.230	31.2	125	22	.37	9.3	46	203	.45	11.4	0.135	3.4	3.33	SST	CG	N
1.500	38.10	3804	1.25	31.8	1.290	32.8	32	5.6	.80	20	26	114	.42	10.7	0.105	2.7	4.00	SPR	CG	Z
1.500	38.10	12635	1.56	39.7	1.184	30.1	185	32	.60	15	110	491	.79	20.1	0.158	4.0	4.00	MW	C	N
1.500	38.10	S-1197	1.75	44.5	1.380	35.1	2.0	.35	1.4	36	2.8	12	.35	8.8	0.060	1.5	4.75	SST	C	N
1.500	38.10	S-3032	1.75	44.5	1.374	34.9	2.5	.44	1.4	36	3.5	16	.34	8.7	0.063	1.6	4.50	SST	C	N
1.500	38.10	11471	1.75	44.5	1.340	34.0	6.3	1.1	1.3	34	8.4	37	.42	10.7	0.080	2.0	5.25	HD	CG	Z
1.500	38.10	12544	1.75	44.5	1.188	30.2	140	25	.61	15	85	380	.86	21.8	0.156	4.0	4.50	OT	C	N
1.500	38.10	10405	1.94	49.2	1.274	32.4	27	4.7	1.1	29	31	137	.59	15.1	0.113	2.9	5.25	SPR	CG	N
1.500	38.10	3647	2.06	52.4	1.376	35.0														




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.500	38.10	32	4.00	101.6	1.230	31.2	24	4.2	2.1	53	51	226	1.32	33.4	0.135	3.4	9.75	HD	CG	Z
1.500	38.10	11514	4.16	105.6	1.282	32.6	11	1.9	2.7	68	29	128	1.09	27.7	0.109	2.8	9.00	SPR	CG	Z
1.500	38.10	3380	4.25	108.0	1.286	32.7	10	1.7	2.7	69	27	121	1.07	27.2	0.107	2.7	9.00	SPR	C	Z
1.500	38.10	S-3167	4.50	114.3	1.300	33.0	7.3	1.3	2.8	72	21	92	.83	21.0	0.100	2.5	8.25	SST	CG	N
1.500	38.10	11976	4.50	114.3	1.260	32.0	22	3.8	1.7	43	37	164	.87	22.1	0.120	3.0	7.25	SPR	CG	Z
1.500	38.10	4259	4.50	114.3	1.012	25.7	321	56	.80	20	257	1143	2.44	62.0	0.244	6.2	10.0	SPR	CG	Z
1.500	38.10	3135	4.56	115.9	1.300	33.0	8.3	1.4	2.7	68	22	99	.83	21.2	0.100	2.5	8.33	SPR	CG	Z
1.500	38.10	12042	4.59	116.7	1.250	31.8	16	2.8	2.6	67	42	185	1.31	33.3	0.125	3.2	10.5	SPR	CG	Z
1.500	38.10	2847	4.88	123.8	1.176	29.9	57	10	1.5	38	85	377	1.50	38.1	0.162	4.1	9.25	SPR	CG	Z
1.500	38.10	7058	5.00	127.0	1.032	26.2	161	28	1.2	30	192	853	3.39	86.2	0.234	5.9	13.5	SST	C	N
1.500	38.10	S-467	5.13	130.2	1.250	31.8	9.8	1.7	3.4	86	33	147	1.75	44.5	0.125	3.2	14.0	SST	CG	N
1.500	38.10	7009	5.88	149.2	1.050	26.7	125	22	1.6	41	203	905	3.90	99.1	0.225	5.7	16.3	HD	C	Z
1.500	38.10	3440	6.00	152.4	1.290	32.8	4.0	.70	4.1	104	17	74	1.89	48.0	0.105	2.7	18.0	SPR	CG	Z
1.500	38.10	3378	6.75	171.5	1.070	27.2	90	16	2.0	52	185	823	3.87	98.3	0.215	5.5	18.0	SPR	CG	Z
1.500	38.10	S-985	6.88	174.6	1.250	31.8	9.0	1.6	4.2	107	38	169	1.88	47.6	0.125	3.2	15.0	SST	CG	N
1.500	38.10	846	8.00	203.2	1.146	29.1	31	5.5	3.5	89	110	489	3.81	96.7	0.177	4.5	21.5	HD	CG	Z
1.500	38.10	12152	8.63	219.1	1.156	29.4	27	4.7	3.8	96	101	449	3.78	96.1	0.172	4.4	22.0	SPR	CG	Z
1.500	38.10	4222	10.0	254.0	1.290	32.8	2.9	.50	7.4	189	21	95	2.57	65.3	0.105	2.7	24.5	SPR	CG	Z
1.500	38.10	10256	10.0	254.0	1.116	28.3	49	8.6	2.7	69	133	592	3.98	101.2	0.192	4.9	19.8	SPR	C	GI
1.500	38.10	863	12.0	304.8	1.230	31.2	7.5	1.3	6.8	172	51	226	3.65	92.6	0.135	3.4	27.0	HD	CG	Z
1.500	38.10	532	12.0	304.8	1.204	30.6	11	1.8	6.3	161	67	296	4.37	110.9	0.148	3.8	28.5	HD	C	Z
1.500	38.10	851	12.0	304.8	1.176	29.9	17	2.9	5.1	130	85	377	4.54	115.2	0.162	4.1	27.0	HD	C	Z
1.500	38.10	842	12.0	304.8	1.116	28.3	29	5.0	4.7	118	133	592	6.24	158.5	0.192	4.9	32.5	HD	CG	Z
1.500	38.10	804	12.0	304.8	1.086	27.6	39	6.9	4.2	107	166	737	6.83	173.5	0.207	5.3	33.0	HD	CG	Z
1.500	38.10	835	12.0	304.8	1.050	26.7	57	9.9	3.6	91	203	905	7.50	190.5	0.225	5.7	33.3	HD	CG	Z
1.515	38.48	12679	1.50	38.1	1.203	30.6	151	26	.50	13	75	334	.82	20.8	0.156	4.0	4.25	SPR	C	N
1.515	38.48	S-989	1.91	48.4	1.135	28.8	204	36	.54	14	110	490	1.05	26.5	0.190	4.8	5.50	SST	CG	N
1.515	38.48	S-288	2.13	54.0	1.371	34.8	2.5	.44	1.7	42	4.1	18	.47	11.9	0.072	1.8	6.50	SST	CG	N
1.515	38.48	11872	2.16	54.8	1.141	29.0	214	38	.57	14	122	543	1.03	26.1	0.187	4.7	5.50	SPR	CG	N
1.515	38.48	11178	2.31	58.7	1.099	27.9	344	60	.48	12	167	741	1.14	29.1	0.208	5.3	5.50	SPR	CG	Z
1.515	38.48	2923	2.50	63.5	1.245	31.6	28	5.0	1.2	30	34	150	1.31	33.2	0.135	3.4	8.67	SPR	C	Z
1.515	38.48	2775	2.50	63.5	1.227	31.2	37	6.5	1.1	29	42	186	1.37	34.7	0.144	3.7	8.50	SPR	C	Z
1.515	38.48	11116	2.50	63.5	1.141	29.0	214	38	.57	14	122	543	1.03	26.1	0.187	4.7	5.50	SPR	CG	N
1.515	38.48	1519	2.75	69.9	1.075	27.3	312	55	.660	16.76	206	922	1.69	42.9	0.225	5.72	7.50	SPR	CG	Z
1.515	38.48	S-3092	3.00	76.2	1.279	32.5	12	2.1	1.8	45	21	93	1.24	31.5	0.118	3.0	9.50	SST	C	N
1.515	38.48	S-109	3.00	76.2	1.015	25.8	322	56	.63	16	201	894	2.38	60.3	0.250	6.4	9.50	SST	CG	N
1.515	38.48	2706	4.84	123.0	1.191	30.3	57	10	1.5	37	84	373	1.46	37.0	0.162	4.1	9.00	SPR	CG	Z
1.515	38.48	3323	6.75	171.5	1.105	28.1	71	12	2.3	57	160	710	3.69	93.7	0.205	5.2	18.0	SPR	CG	Z
1.515	38.48	3418	6.75	171.5	1.075	27.3	97	17	1.9	50	189	840	3.96	100.6	0.220	5.6	18.0	SPR	CG	Z
1.515	38.48	3414	8.50	215.9	1.065	27.1	86	15	2.3	60	202	897	4.95	125.7	0.225	5.7	22.0	SPR	CG	Z
1.531	38.89	11262	1.19	30.2	1.247	31.7	77	14	.55	14	42	189	.64	16.2	0.142	3.6	4.50	SST	CG	N
1.531	38.89	11155	1.25	31.8	1.247	31.7	97	17	.60	15	58	257	.60	15.3	0.142	3.6	4.25	SPR	CG	Z
1.531	38.89	S-1648	1.41	35.7	1.321	33.6	21	3.7	.93	24	20	89	.47	12.0	0.105	2.7	4.50	SST	CG	N
1.531	38.89	1675	1.50	38.1	1.399	35.5	3.3	.57	1.1	29	3.7	16	.37	9.5	0.066	1.7	4.67	SPR	C	Z
1.531	38.89	10648	1.63	41.3	1.371	34.8	6.4	1.1	1.2	31	7.9	35	.40	10.2	0.080	2.0	5.00	SPR	CG	Z
1.531	38.89	S-85	2.00	50.8	1.387	35.2	3.9	.69	1.6	40	6.2	28	.41	10.5	0.072	1.8	4.75	SST	C	N
1.531	38.89	S-405	2.00	50.8	1.147	29.1	202	35	.56	14	113	501	1.06	26.8	0.192	4.9	5.50	SST	CG	N
1.531	38.89	11152	2.19	55.6	1.091	27.7	498	87	.38	9.5	187	832	1.10	27.9	0.220	5.6	5.00	SPR	CG	Z
1.531	38.89	4397	2.22	56.4	1.321	33.6	13	2.2	1.5	38	19	85	.71	18.0	0.105	2.7	6.75	SPR	CG	N
1.531	38.89	10391	2.25	57.2	1.105	28.1	431	75	.41	10	177	787	1.07	27.1	0.213	5.4	5.00	SPR	CG	Z
1.531	38.89	10319	2.44	61.9	1.117	28.4	284	50	.57	15	163	724	1.24	31.5	0.207	5.3	6.00	SPR	CG	Z
1.531	38.89	10835	3.00	76.2	1.305	33.1	17	3.0	1.6	41	28	123	.71	17.9	0.113	2.9	6.25	SST	CG	N
1.531	38.89	4242	3.00	76.2	1.207	30.7	110	19	.75	19	83	370	.89	22.6	0.162	4.1	5.50	SPR	CG	Z
1.531	38.89	S-3111	3.38	85.7	1.321	33.6	12	2.0	2.0	51	23	104	.68	17.3	0.105	2.7	6.50	SST	CG	N
1.531	38.89	4115	4.25	108.0	.907	23.0	1003	176	.48	12	478	2128	2.96	75.3	0.312	7.9	9.50	SPR	CG	Z
1.531	38.89	S-449	6.50	165.1	1.147	29.1	46	8.0												



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.562	39.67	11177	2.56	65.1	1.188	30.2	225	39	.53	13	119	528	.94	23.7	0.187	4.7	5.00	SPR	CG	Z
1.562	39.67	11996	2.63	66.7	.876	22.3	2312	405	.26	6.6	599	2665	2.32	58.8	0.343	8.7	6.75	SPR	CG	Z
1.562	39.67	852	2.75	69.9	1.238	31.4	69	12	1.2	30	82	363	1.17	29.8	0.162	4.1	7.25	HD	CG	Z
1.562	39.67	S-314	3.16	80.2	1.436	36.5	2.1	.37	2.6	66	5.6	25	.36	9.2	0.063	1.6	4.75	SST	C	N
1.562	39.67	4346	3.63	92.1	1.178	29.9	76	13	1.3	34	100	446	2.30	58.5	0.192	4.9	12.0	SPR	CG	Z
1.562	39.67	895	4.00	101.6	.996	25.3	497	87	.74	19	367	1633	3.08	78.2	0.283	7.2	11.0	HD	CG	Z
1.562	39.67	812	4.25	108.0	1.208	30.7	57	10	1.9	47	106	471	2.01	51.0	0.177	4.5	11.3	HD	CG	Z
1.562	39.67	678	4.38	111.1	1.076	27.3	213	37	1.2	29	245	1090	2.98	75.6	0.243	6.2	12.3	HD	CG	Z
1.562	39.67	11669	4.84	123.0	1.478	37.5	.07	.01	4.0	103	.30	1.3	.80	20.3	0.042	1.1	19.0	SPR	CG	N
1.562	39.67	3244	5.00	127.0	1.202	30.5	54	9.5	2.0	50	106	472	2.25	57.2	0.180	4.6	12.5	SPR	CG	Z
1.562	39.67	10570	5.00	127.0	1.108	28.1	153	27	1.3	33	201	895	3.07	77.9	0.227	5.8	12.5	SPR	C	Z
1.562	39.67	S-3110	5.50	139.7	1.380	35.1	4.7	.82	3.2	81	15	67	.71	17.9	0.091	2.3	7.75	SST	CG	N
1.562	39.67	11509	6.41	162.7	1.260	32.0	20	3.5	3.3	84	66	295	2.47	62.6	0.151	3.8	15.3	SPR	CG	Z
1.562	39.67	911	7.50	190.5	1.266	32.2	15	2.6	4.3	110	64	285	2.74	69.5	0.148	3.8	18.5	HD	CG	Z
1.562	39.67	2735	11.4	290.5	1.362	34.6	2.9	.51	7.3	186	21	95	1.78	45.1	0.100	2.5	17.8	SPR	CG	Z
1.578	40.08	12276	1.00	25.4	1.496	38.0	.37	.07	.75	19	.28	1.3	.25	6.2	0.041	1.0	5.00	SPR	C	Z
1.578	40.08	11148	1.25	31.8	1.266	32.2	169	30	.43	11	72	322	.59	14.9	0.156	4.0	3.75	SPR	CG	Z
1.578	40.08	3358	1.31	33.3	1.204	30.6	435	76	.27	6.9	118	523	.65	16.6	0.187	4.7	3.50	SPR	CG	Z
1.578	40.08	10349	1.56	39.7	1.368	34.7	14	2.4	.93	24	13	57	.63	16.0	0.105	2.7	6.00	SPR	CG	Z
1.578	40.08	S-162	1.63	41.3	1.426	36.2	2.9	.51	1.2	29	3.3	15	.48	12.1	0.076	1.9	6.25	SST	CG	N
1.578	40.08	S-3227	1.72	43.6	1.394	35.4	5.6	.97	1.1	27	6.0	27	.64	16.4	0.092	2.3	7.00	SST	CG	N
1.578	40.08	11774	2.38	60.3	1.462	37.1	1.9	.32	2.1	54	3.9	17	.26	6.6	0.058	1.5	4.50	SPR	CG	Z
1.578	40.08	10329	2.44	61.9	1.164	29.6	241	42	.66	17	158	704	1.29	32.9	0.207	5.3	6.25	SPR	CG	Z
1.578	40.08	11629	2.50	63.5	1.338	34.0	14	2.4	1.4	36	20	87	1.08	27.4	0.120	3.0	9.00	SPR	CG	Z
1.578	40.08	S-3189	3.00	76.2	1.308	33.2	28	4.8	1.6	40	44	194	.95	24.0	0.135	3.4	7.00	SST	CG	N
1.578	40.08	10689	3.38	85.7	1.458	37.0	.74	.13	2.8	70	2.0	9.0	.62	15.6	0.060	1.5	9.25	SPR	C	Z
1.578	40.08	3486	3.75	95.3	1.328	33.7	16	2.9	2.4	62	40	176	1.13	28.6	0.125	3.2	9.00	HD	CG	Z
1.578	40.08	S-298	4.16	105.6	1.404	35.7	4.8	.84	2.8	72	14	61	.57	14.4	0.087	2.2	6.50	SST	CG	N
1.578	40.08	S-3193	6.75	171.5	1.398	35.5	1.7	.30	5.2	133	8.8	39	1.53	38.9	0.090	2.3	17.0	SST	CG	N
1.578	40.08	11965	7.69	195.2	1.190	30.2	52	9.1	2.5	64	131	583	3.1	78.7	0.192	4.9	16.1	SPR	CG	GI
1.580	40.13	72864	2.50	63.5	1.166	29.6	210	37	1.1	27	223	994	1.42	36.1	0.207	5.3	6.88	MW	CG	N
1.580	40.13	72864S	2.50	63.5	1.166	29.6	179	31	.76	19	136	606	1.42	36.1	0.207	5.3	6.88	SST	CG	N
1.580	40.13	72865	3.00	76.2	1.166	29.6	170	30	1.3	33	223	994	1.66	42.1	0.207	5.3	8.00	MW	CG	N
1.580	40.13	72865S	3.00	76.2	1.166	29.6	145	25	.94	24	136	606	1.66	42.1	0.207	5.3	8.00	SST	CG	N
1.580	40.13	72866	3.50	88.9	1.166	29.6	142	25	1.6	40	223	994	1.89	48.0	0.207	5.3	9.13	MW	CG	N
1.580	40.13	72866S	3.50	88.9	1.166	29.6	121	21	1.1	29	136	606	1.89	48.0	0.207	5.3	9.13	SST	CG	N
1.580	40.13	72867	4.00	101.6	1.166	29.6	121	21	1.8	47	223	994	2.15	54.5	0.207	5.3	10.4	MW	CG	N
1.580	40.13	72867S	4.00	101.6	1.166	29.6	103	18	1.3	34	136	606	2.15	54.5	0.207	5.3	10.4	SST	CG	N
1.580	40.13	72868	4.50	114.3	1.166	29.6	107	19	2.1	53	223	994	2.38	60.5	0.207	5.3	11.5	MW	CG	N
1.580	40.13	72868S	4.50	114.3	1.166	29.6	91	16	1.5	38	136	606	2.38	60.5	0.207	5.3	11.5	SST	CG	N
1.580	40.13	72869	5.00	127.0	1.166	29.6	95	17	2.4	60	223	994	2.64	67.0	0.207	5.3	12.8	MW	CG	N
1.580	40.13	72869S	5.00	127.0	1.166	29.6	81	14	1.7	43	136	606	2.64	67.0	0.207	5.3	12.8	SST	CG	N
1.580	40.13	72870	5.50	139.7	1.166	29.6	86	15	2.6	66	223	994	2.87	73.0	0.207	5.3	13.9	MW	CG	N
1.580	40.13	72870S	5.50	139.7	1.166	29.6	73	13	1.9	47	136	606	2.87	73.0	0.207	5.3	13.9	SST	CG	N
1.580	40.13	72871	6.00	152.4	1.166	29.6	79	14	2.8	72	223	994	3.08	78.2	0.207	5.3	14.9	MW	CG	N
1.580	40.13	72871S	6.00	152.4	1.166	29.6	67	12	2.0	52	136	606	3.08	78.2	0.207	5.3	14.9	SST	CG	N
1.593	40.46	11608	1.88	47.6	1.181	30.0	243	42	.43	11	105	467	1.44	36.6	0.206	5.2	6.00	SPR	CG	Z
1.593	40.46	S-1600	2.25	57.2	1.347	34.2	15	2.7	1.1	29	18	78	1.11	28.1	0.123	3.1	8.00	SST	CG	N
1.593	40.46	3428	2.50	63.5	1.343	34.1	16	2.8	1.4	35	22	97	1.13	28.6	0.125	3.2	9.00	HD	CG	Z
1.593	40.46	S-991	2.63	66.7	1.417	36.0	7.3	1.3	1.9	48	14	62	.44	11.2	0.088	2.2	5.00	SST	CG	N
1.593	40.46	10825	4.25	108.0	1.351	34.3	19	3.4	1.8	47	36	159	.97	24.6	0.121	3.1	7.00	SPR	C	Z
1.593	40.46	3641	5.00	127.0	1.453	36.9	1.2	.21	4.3	109	5.3	23	.70	17.8	0.070	1.8	10.0	HD	CG	Z
1.593	40.46	3109	5.13	130.2	1.343	34.1	11	1.9	3.5	89	39	173	1.63	41.3	0.125	3.2	12.0	SPR	C	Z
1.593	40.46	S-359	5.13	130.2	1.179	29.9	108	19	1.3	32	135	601	2.07	52.6	0.207	5.3	10.0	SST	CG	N
1.609	40.87	10451	1.28	32.5	1.277	32.4	208	36	.41	10	85	379	.62	15.8	0.166	4.2	3.75	SPR	CG	Z
1.609	40.87	2717	1.56																	



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.625	41.28	12725	4.30	109.2	1.443	36.7	3.0	.53	3.2	81	9.7	43	1.09	27.7	0.091	2.3	11.0	HD	C	N
1.625	41.28	369	4.50	114.3	1.139	28.9	200	35	1.2	30	237	1053	2.79	71.0	0.243	6.2	11.5	HD	CG	Z
1.625	41.28	2793	5.63	142.9	1.343	34.1	13	2.3	3.5	89	47	209	2.12	53.7	0.141	3.6	15.0	SPR	CG	GI
1.625	41.28	10393	7.25	184.2	1.137	28.9	119	21	2.0	51	239	1065	4.45	113.1	0.244	6.2	18.3	SPR	CG	Z
1.625	41.28	843	12.0	304.8	1.241	31.5	24	4.2	5.1	130	124	550	5.66	143.9	0.192	4.9	29.5	HD	CG	Z
1.640	41.66	S-1465	1.38	34.9	1.464	37.2	13	2.3	.98	25	13	58	.40	10.1	0.088	2.2	3.50	SST	C	N
1.640	41.66	B17-193	1.47	37.3	1.280	32.5	215	38	.41	10	87	389	.72	18.3	0.180	4.6	4.00	SST	CG	N
1.640	41.66	S-965	1.69	42.8	1.344	34.1	60	11	.92	23	55	245	.74	18.8	0.148	3.8	5.00	SST	CG	N
1.640	41.66	3008	1.88	47.6	1.496	38.0	4.0	.70	1.6	39	6.2	28	.32	8.2	0.072	1.8	4.50	SPR	CG	GI
1.640	41.66	3105	2.00	50.8	1.370	34.8	49	8.5	.96	24	47	207	.66	16.7	0.135	3.4	5.00	SPR	CG	Z
1.640	41.66	S-1666	2.25	57.2	1.370	34.8	41	7.3	1.0	26	42	187	.68	17.1	0.135	3.4	5.00	SST	CG	N
1.640	41.66	3239	2.25	57.2	1.286	32.7	120	21	.84	21	101	450	1.02	25.9	0.177	4.5	5.75	SPR	CG	Z
1.640	41.66	S-3237	2.34	59.5	1.390	35.3	20	3.5	1.5	39	30	135	.81	20.6	0.125	3.2	6.50	SST	CG	N
1.640	41.66	10665	2.38	60.3	1.190	30.2	433	76	.43	11	188	835	1.13	28.6	0.225	5.7	5.00	SPR	CG	Z
1.640	41.66	S-102	3.25	82.6	1.328	33.7	38	6.6	1.6	42	62	275	1.25	31.7	0.156	4.0	8.00	SST	CG	N
1.640	41.66	4193	3.25	82.6	1.016	25.8	969	170	.47	12	452	2011	2.50	63.4	0.312	7.9	8.00	SPR	CG	Z
1.640	41.66	2990	3.38	85.7	1.476	37.5	3.4	.60	2.7	69	9.3	42	.66	16.7	0.082	2.1	7.00	SPR	C	Z
1.640	41.66	S-319	3.63	92.1	1.300	33.0	43	7.5	1.9	47	80	355	1.64	41.7	0.170	4.3	9.67	SST	CG	N
1.640	41.66	S-1188	3.75	95.3	1.506	38.3	1.3	.23	3.2	82	4.2	19	.54	13.6	0.067	1.7	7.00	SST	C	N
1.640	41.66	3174	4.00	101.6	1.506	38.3	.99	.17	3.3	84	3.3	15	.70	17.9	0.067	1.7	9.50	SPR	C	Z
1.640	41.66	1861	4.31	109.5	1.370	34.8	18	3.2	2.6	66	47	207	1.32	33.4	0.135	3.4	9.75	HD	CG	Z
1.640	41.66	1833	4.78	121.4	1.324	33.6	46	8.0	1.6	40	72	322	1.26	32.1	0.158	4.0	8.00	HD	CG	GI
1.640	41.66	3307	5.75	146.1	1.286	32.7	41	7.2	2.5	63	101	450	2.30	58.4	0.177	4.5	13.0	SPR	CG	Z
1.640	41.66	4404	8.00	203.2	1.430	36.3	4.6	.81	5.1	130	24	105	1.42	36.0	0.105	2.7	12.5	SPR	C	GI
1.656	42.06	10529	1.16	29.4	1.430	36.3	51	8.9	.55	14	28	125	.37	9.3	0.113	2.9	3.25	SPR	CG	Z
1.656	42.06	11542	2.03	51.6	1.416	36.0	18	3.2	1.1	29	21	92	.90	22.9	0.120	3.0	6.50	SPR	CG	GI
1.656	42.06	10373	2.38	60.3	1.206	30.6	457	80	.41	10	186	827	1.07	27.2	0.225	5.7	4.75	SPR	CG	Z
1.656	42.06	S-283	2.88	73.0	1.406	35.7	21	3.7	1.6	41	35	154	.75	19.1	0.125	3.2	6.00	SST	CG	N
1.656	42.06	S-1642	9.19	233.4	1.092	27.7	154	27	1.9	47	286	1270	6.27	159.4	0.282	7.2	22.3	SST	CG	N
1.672	42.47	12618	4.00	101.6	1.318	33.5	42	7.3	1.9	49	81	358	2.08	52.8	0.177	4.5	10.8	SST	C	N
1.687	42.85	S-3070	1.38	34.9	1.531	38.9	3.7	.65	.91	23	3.4	15	.47	11.9	0.078	2.0	5.00	SST	C	N
1.687	42.85	1948	1.50	38.1	1.531	38.9	4.3	.75	1.1	28	4.7	21	.39	9.9	0.078	2.0	5.00	SPR	CG	Z
1.687	42.85	72872	1.50	38.1	1.417	36.0	64	11	.96	24	62	275	.54	13.7	0.135	3.4	4.00	MW	CG	N
1.687	42.85	72872S	1.50	38.1	1.417	36.0	55	9.6	.75	19	41	182	.54	13.7	0.135	3.4	4.00	SST	CG	N
1.687	42.85	72880	1.50	38.1	1.391	35.3	90	16	.89	23	80	355	.61	15.5	0.148	3.8	4.13	MW	CG	N
1.687	42.85	72880S	1.50	38.1	1.391	35.3	76	13	.70	18	54	239	.61	15.5	0.148	3.8	4.13	SST	CG	N
1.687	42.85	72882	1.50	38.1	1.375	34.9	112	20	.85	22	95	423	.64	16.3	0.156	4.0	4.13	MW	CG	N
1.687	42.85	72882S	1.50	38.1	1.375	34.9	95	17	.63	16	60	268	.64	16.3	0.156	4.0	4.13	SST	CG	N
1.687	42.85	72897	1.50	38.1	1.363	34.6	126	22	.81	21	102	454	.69	17.5	0.162	4.1	4.25	MW	CG	N
1.687	42.85	72897S	1.50	38.1	1.363	34.6	107	19	.63	16	67	300	.69	17.5	0.162	4.1	4.25	SST	CG	N
1.687	42.85	72898	1.50	38.1	1.333	33.9	178	31	.75	19	133	591	.75	19.1	0.177	4.5	4.25	MW	CG	N
1.687	42.85	72898S	1.50	38.1	1.333	33.9	151	26	.58	15	87	389	.75	19.1	0.177	4.5	4.25	SST	CG	N
1.687	42.85	72909	1.50	38.1	1.303	33.1	247	43	.66	17	163	726	.84	21.3	0.192	4.9	4.38	MW	CG	N
1.687	42.85	72909S	1.50	38.1	1.303	33.1	210	37	.49	12	103	457	.84	21.3	0.192	4.9	4.38	SST	CG	N
1.687	42.85	365	1.88	47.6	1.333	33.9	142	25	.69	18	98	438	.86	21.9	0.177	4.5	5.00	HD	CG	Z
1.687	42.85	11380	2.00	50.8	1.505	38.2	12	2.2	1.1	29	14	62	.34	8.7	0.091	2.3	3.75	SST	CG	N
1.687	42.85	72873	2.00	50.8	1.417	36.0	46	8.0	1.4	35	62	277	.64	16.3	0.135	3.4	4.75	MW	CG	N
1.687	42.85	72873S	2.00	50.8	1.417	36.0	39	6.8	1.0	27	41	182	.64	16.3	0.135	3.4	4.75	SST	CG	N
1.687	42.85	72884	2.00	50.8	1.375	34.9	79	14	1.2	31	95	423	.78	19.8	0.156	4.0	5.00	MW	CG	N
1.687	42.85	72884S	2.00	50.8	1.375	34.9	67	12	.90	23	60	268	.78	19.8	0.156	4.0	5.00	SST	CG	N
1.687	42.85	72899	2.00	50.8	1.333	33.9	124	22	1.0	27	130	577	.95	24.2	0.177	4.5	5.38	MW	CG	N
1.687	42.85	72899S	2.00	50.8	1.333	33.9	105	18	.83	21	87	389	.95	24.2	0.177	4.5	5.38	SST	CG	N
1.687	42.85	72910	2.00	50.8	1.303	33.1	171	30	.97	25	165	736	1.03	26.2	0.192	4.9	5.38	MW	CG	N
1.687	42.85	72910S	2.00	50.8	1.303	33.1	145	25	.71	18	103	457	1.03	26.2	0.192	4.9	5.38	SST	CG	N
1.687	42.85	S-3065	2.25	57.2	1.407	35.7	43	7.6	1.1	27	46	202	.70	17.8	0.140	3.6	5.00	SST	CG	N
1.687	42.85	72874	2.50	63.5	1.417	36.0	36	6.2	1.7	44	62	275	.76	19.3	0.135	3.4				




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	F S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.687	42.85	11253	3.00	76.2	1.201	30.5	290	51	.79	20	229	1018	1.88	47.8	0.243	6.2	7.75	SPR	CG	Z
1.687	42.85	72876	3.50	88.9	1.417	36.0	25	4.3	2.5	64	62	275	.98	24.9	0.135	3.4	7.25	MW	CG	N
1.687	42.85	72876S	3.50	88.9	1.417	36.0	21	3.6	2.0	50	41	182	.98	24.9	0.135	3.4	7.25	SST	CG	N
1.687	42.85	72890	3.50	88.9	1.375	34.9	42	7.3	2.3	58	95	423	1.19	30.2	0.156	4.0	7.63	MW	CG	N
1.687	42.85	72890S	3.50	88.9	1.375	34.9	36	6.2	1.7	43	60	268	1.19	30.2	0.156	4.0	7.63	SST	CG	N
1.687	42.85	72905	3.50	88.9	1.333	33.9	66	12	2.1	52	137	609	1.44	36.5	0.177	4.5	8.13	MW	CG	N
1.687	42.85	72905S	3.50	88.9	1.333	33.9	56	9.9	1.5	39	87	389	1.44	36.5	0.177	4.5	8.13	SST	CG	N
1.687	42.85	72913	3.50	88.9	1.303	33.1	89	16	1.8	47	163	727	1.66	42.1	0.192	4.9	8.63	MW	CG	N
1.687	42.85	72913S	3.50	88.9	1.303	33.1	75	13	1.4	35	103	457	1.66	42.1	0.192	4.9	8.63	SST	CG	N
1.687	42.85	72919	3.50	88.9	1.251	31.8	152	27	1.6	40	242	1077	1.91	48.5	0.218	5.5	8.75	MW	CG	N
1.687	42.85	72919S	3.50	88.9	1.251	31.8	129	23	1.2	29	149	663	1.91	48.5	0.218	5.5	8.75	SST	CG	N
1.687	42.85	72927	3.50	88.9	1.219	31.0	208	36	1.4	36	292	1299	2.05	52.0	0.234	5.9	8.75	MW	CG	N
1.687	42.85	72927S	3.50	88.9	1.219	31.0	176	31	.98	25	173	768	2.05	52.0	0.234	5.9	8.75	SST	CG	N
1.687	42.85	72877	4.00	101.6	1.417	36.0	21	3.7	2.9	74	62	275	1.08	27.4	0.135	3.4	8.00	MW	CG	N
1.687	42.85	72877S	4.00	101.6	1.417	36.0	18	3.2	2.3	58	41	182	1.08	27.4	0.135	3.4	8.00	SST	CG	N
1.687	42.85	72892	4.00	101.6	1.375	34.9	36	6.3	2.6	67	95	423	1.35	34.2	0.156	4.0	8.63	MW	CG	N
1.687	42.85	72892S	4.00	101.6	1.375	34.9	31	5.4	2.0	50	60	268	1.35	34.2	0.156	4.0	8.63	SST	CG	N
1.687	42.85	72906	4.00	101.6	1.333	33.9	56	9.8	2.3	59	131	581	1.66	42.1	0.177	4.5	9.38	MW	CG	N
1.687	42.85	72906S	4.00	101.6	1.333	33.9	47	8.3	1.8	47	87	389	1.66	42.1	0.177	4.5	9.38	SST	CG	N
1.687	42.85																			




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.718	43.64	4315	3.50	88.9	1.344	34.1	75	13	1.4	37	109	483	1.59	40.4	0.187	4.7	8.50	SPR	CG	Z
1.718	43.64	S-1507	5.00	127.0	1.594	40.5	.71	.12	4.5	115	3.2	14	.48	12.2	0.062	1.6	7.75	SST	CG	N
1.718	43.64	3934	5.00	127.0	1.558	39.6	1.7	.29	4.1	105	6.9	31	.88	22.4	0.080	2.0	10.0	SPR	C	Z
1.718	43.64	2525	5.00	127.0	1.548	39.3	2.2	.38	4.1	103	8.8	39	.94	23.7	0.085	2.2	10.0	SPR	C	Z
1.718	43.64	4337	5.50	139.7	1.094	27.8	577	101	.75	19	435	1934	3.28	83.2	0.312	7.9	10.5	SPR	CG	Z
1.718	43.64	S-1622	6.13	155.6	1.518	38.6	3.6	.63	5.0	127	18	80	1.03	26.2	0.100	2.5	10.3	SST	CG	N
1.718	43.64	238	7.00	177.8	1.422	36.1	15	2.7	3.9	98	59	260	2.04	51.7	0.148	3.8	13.8	SPR	CG	Z
1.718	43.64	3176	8.75	222.3	1.500	38.1	4.2	.74	5.9	151	25	112	1.47	37.4	0.109	2.8	13.0	SPR	CG	Z
1.734	44.04	12130	1.56	39.7	1.284	32.6	460	81	.39	9.8	178	793	.97	24.7	0.225	5.7	4.33	SPR	CG	Z
1.734	44.04	1669	2.00	50.8	1.324	33.6	178	31	.77	20	137	608	1.23	31.2	0.205	5.2	6.00	SPR	CG	Z
1.734	44.04	S-3044	2.25	57.2	1.464	37.2	25	4.4	1.4	37	37	163	.81	20.6	0.135	3.4	6.00	SST	CG	N
1.734	44.04	11285	2.38	60.3	1.552	39.4	4.6	.81	1.7	44	8.0	35	.66	16.8	0.091	2.3	6.25	SST	C	N
1.734	44.04	10361	2.50	63.5	1.284	32.6	238	42	.75	19	178	793	1.46	37.2	0.225	5.7	6.50	SPR	CG	Z
1.734	44.04	1595	3.38	85.7	1.010	25.7	1821	319	.40	10	722	3209	2.63	66.7	0.362	9.2	7.25	OT	CG	Z
1.734	44.04	S-382	3.44	87.3	1.576	40.0	2.1	.38	2.8	71	6.0	27	.63	16.1	0.079	2.0	7.00	SST	C	N
1.734	44.04	4191	3.75	95.3	1.414	35.9	30	5.3	2.2	55	65	289	1.60	40.6	0.160	4.1	10.0	SPR	CG	GI
1.734	44.04	11793	5.47	138.9	1.094	27.8	627	110	.74	19	464	2062	3.84	97.5	0.320	8.1	10.5	SPR	CG	Z
1.734	44.04	12550	5.47	138.9	1.110	28.2	474	83	.91	23	431	1918	3.74	95.1	0.312	7.9	12.0	SPR	CG	Z
1.734	44.04	12681	5.50	139.7	1.072	27.2	625	109	.82	21	510	2269	3.97	100.9	0.331	8.4	12.0	SPR	CG	Z
1.734	44.04	S-967	6.38</																	



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.781	45.24	S-1005	6.75	171.5	1.557	39.5	6.0	1.1	3.8	98	23	103	1.01	25.6	0.112	2.8	9.00	SST	CG	N
1.781	45.24	S-3083	16.0	406.4	1.511	38.3	3.4	.59	9.8	248.9	32.9	147	4.01	101.8	0.135	3.4	29.7	SST	CG	N
1.796	45.62	4153	3.00	76.2	1.662	42.2	1.4	.25	2.5	64	3.5	16	.47	11.9	0.067	1.7	6.00	SPR	C	Z
1.796	45.62	12168	3.47	88.1	1.306	33.2	198	35	1.1	28	221	985	2.21	56.0	0.245	6.2	9.00	SPR	CG	Z
1.796	45.62	10906	3.50	88.9	1.530	38.9	12	2.1	2.6	67	31	138	.86	22.0	0.133	3.4	6.50	PB	CG	N
1.796	45.62	B17-198	4.00	101.6	1.640	41.7	1.5	.26	3.3	83	4.8	21	.73	18.5	0.078	2.0	8.33	SST	C	N
1.796	45.62	3494	4.38	111.1	1.296	32.9	190	33	1.2	31	235	1044	2.50	63.5	0.250	6.4	10.0	SPR	CG	Z
1.796	45.62	S-983	5.00	127.0	1.472	37.4	38	6.6	1.7	43	63	282	1.17	29.8	0.162	4.1	7.25	SST	CG	N
1.796	45.62	11854	6.50	165.1	1.576	40.0	6.3	1.1	3.8	97	24	107	.99	25.1	0.110	2.8	9.00	SPR	CG	N
1.796	45.62	1621	11.0	279.4	1.416	36.0	23	4.0	4.8	123	109	486	4.18	106.2	0.190	4.8	22.0	HD	CG	Z
1.812	46.02	11994	1.25	31.8	1.516	38.5	75	13	.66	17	49	219	.59	15.0	0.148	3.8	4.00	SPR	CG	Z
1.812	46.02	2758	2.31	58.7	1.542	39.2	22	3.8	1.4	34	29	130	.96	24.4	0.135	3.4	7.00	SPR	CG	Z
1.812	46.02	1583	3.03	77.0	1.692	43.0	.69	.12	2.6	65	1.8	7.9	.48	12.2	0.060	1.5	7.00	SPR	C	Z
1.812	46.02	4349	3.25	82.6	1.542	39.2	20	3.5	2.1	53	42	188	.95	24.0	0.135	3.4	7.00	SPR	CG	Z
1.812	46.02	11115	3.34	84.9	1.342	34.1	186	33	1.0	27	194	865	1.88	47.8	0.235	6.0	8.00	SPR	CG	Z
1.812	46.02	S-3171	3.38	85.7	1.362	34.6	160	28	.90	23	144	641	1.80	45.7	0.225	5.7	7.00	SST	CG	N
1.812	46.02	10478	3.50	88.9	1.342	34.1	194	34	1.0	25	194	865	1.82	46.3	0.235	6.0	7.75	SPR	CG	Z
1.812	46.02	3081	6.00	152.4	1.428	36.3	51	8.9	2.2	56	112	497	2.11	53.6	0.192	4.9	11.0	SPR	CG	Z
1.812	46.02	3298	6.00	152.4	1.392	35.4	68	12	2.1	54	145	646	2.52	64.0	0.210	5.3	12.0	SPR	CG	Z
1.812	46.02	10990	6.50	165.1	1.428															



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.906	48.41	S-978	4.25	108.0	1.636	41.6	14	2.5	2.6	66	36	162	.99	25.1	0.135	3.4	7.33	SST	CG	N
1.906	48.41	11646	5.75	146.1	1.662	42.2	56	9.8	.55	14	31	137	.37	9.3	0.122	3.1	3.00	SPR	CG	Z
1.906	48.41	3281	6.13	155.6	1.420	36.1	141	25	1.4	37	205	911	2.45	62.2	0.243	6.2	10.0	SPR	CG	Z
1.906	48.41	3148	7.00	177.8	1.532	38.9	35	6.2	2.8	71	99	438	2.26	57.3	0.187	4.7	12.0	SPR	CG	Z
1.906	48.41	3417	7.50	190.5	1.340	34.0	160	28	1.9	49	309	1372	4.39	111.4	0.283	7.2	15.5	SPR	CG	Z
1.906	48.41	10088	8.75	222.3	1.562	39.7	21	3.7	3.8	98	81	359	2.32	59.0	0.172	4.4	13.5	SPR	CG	Z
1.906	48.41	3098	9.31	236.5	1.456	37.0	48	8.4	3.4	87	163	727	4.11	104.3	0.225	5.7	18.3	SPR	CG	Z
1.921	48.79	3142	.75	19.1	1.721	43.7	24	4.2	.45	11	11	48	.30	7.6	0.100	2.5	3.00	SPR	CG	Z
1.921	48.79	3330	1.00	25.4	1.731	44.0	19	3.4	.72	18	14	61	.29	7.2	0.095	2.4	3.00	SPR	CG	Z
1.921	48.79	11861	1.66	42.1	1.609	40.9	92	16	.58	15	53	237	.55	13.9	0.156	4.0	3.50	SST	CG	N
1.921	48.79	S-988	1.69	42.8	1.597	40.6	47	8.3	.82	21	39	174	.86	21.9	0.162	4.1	5.33	SST	CG	N
1.921	48.79	S-941	2.25	57.2	1.739	44.2	4.7	.82	1.7	43	7.9	35	.55	13.9	0.091	2.3	5.00	SST	C	N
1.921	48.79	3310	4.25	108.0	1.651	41.9	14	2.4	2.9	73	40	178	1.08	27.4	0.135	3.4	8.00	SPR	CG	Z
1.921	48.79	S-379	4.25	108.0	1.651	41.9	9.1	1.6	2.9	74	26	118	1.35	34.3	0.135	3.4	10.0	SST	CG	N
1.921	48.79	11505	8.75	222.3	1.577	40.1	21	3.6	3.9	98	80	356	2.46	62.6	0.172	4.4	13.3	SPR	CG	Z
1.921	48.79	4054	22.5	571.5	1.471	37.4	18	3.1	9.0	229	162	722	10.1	257.2	0.225	5.7	44.0	SPR	C	Z
1.937	49.20	12114	1.50	38.1	1.563	39.7	109	19	.57	14	62	274	.94	23.7	0.187	4.7	5.00	SPR	CG	Z
1.937	49.20	72933	2.00	50.8	1.641	41.7	52	9.0	1.4	34	70	310	.65	16.4	0.148	3.8	4.38	MW	CG	N
1.937	49.20	72933S	2.00	50.8	1.641	41.7	44	7.7	1.1	27	47	209	.65	16.4	0.148	3.8	4.38	SST	CG	N
1.937	49.20	72942	2.00	50.8	1.6															





O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.937	49.20	72950S	4.00	101.6	1.625	41.3	25	4.3	2.1	54	53	235	1.11	28.2	0.156	4.0	7.13	SST	CG	N
1.937	49.20	72963	4.00	101.6	1.613	41.0	32	5.7	2.8	71	90	400	1.22	30.9	0.162	4.1	7.50	MW	CG	N
1.937	49.20	72963S	4.00	101.6	1.613	41.0	27	4.8	2.2	55	59	263	1.22	30.9	0.162	4.1	7.50	SST	CG	N
1.937	49.20	72970	4.00	101.6	1.583	40.2	44	7.7	2.6	66	115	511	1.39	35.4	0.177	4.5	7.88	MW	CG	N
1.937	49.20	72970S	4.00	101.6	1.583	40.2	37	6.6	2.0	52	77	341	1.39	35.4	0.177	4.5	7.88	SST	CG	N
1.937	49.20	72980	4.00	101.6	1.553	39.4	59	10	2.4	61	143	637	1.58	40.2	0.192	4.9	8.25	MW	CG	N
1.937	49.20	72980S	4.00	101.6	1.553	39.4	50	8.8	1.8	46	90	402	1.58	40.2	0.192	4.9	8.25	SST	CG	N
1.937	49.20	72988	4.00	101.6	1.523	38.7	82	14	2.3	57	185	823	1.71	43.4	0.207	5.3	8.25	MW	CG	N
1.937	49.20	72988S	4.00	101.6	1.523	38.7	70	12	1.6	41	113	501	1.71	43.4	0.207	5.3	8.25	SST	CG	N
1.937	49.20	73000	4.00	101.6	1.487	37.8	112	20	2.0	52	229	1020	1.91	48.6	0.225	5.7	8.50	MW	CG	N
1.937	49.20	73000S	4.00	101.6	1.487	37.8	95	17	1.4	36	136	603	1.91	48.6	0.225	5.7	8.50	SST	CG	N
1.937	49.20	73012	4.00	101.6	1.437	36.5	169	30	1.8	45	302	1342	2.22	56.4	0.250	6.4	8.88	MW	CG	N
1.937	49.20	73012S	4.00	101.6	1.437	36.5	144	25	1.3	33	184	820	2.22	56.4	0.250	6.4	8.88	SST	CG	N
1.937	49.20	3420	4.44	112.7	1.371	34.8	254	45	1.2	30	304	1352	2.83	71.9	0.283	7.2	10.0	SPR	CG	BO
1.937	49.20	72938	4.50	114.3	1.641	41.7	21	3.7	3.4	85	70	312	1.15	29.1	0.148	3.8	7.75	MW	MW	CG
1.937	49.20	72938S	4.50	114.3	1.641	41.7	18	3.1	2.6	67	47	209	1.15	29.1	0.148	3.8	7.75	SST	CG	N
1.937	49.20	72952	4.50	114.3	1.625	41.3	26	4.5	3.2	82	83	371	1.23	31.2	0.156	4.0	7.88	MW	CG	N
1.937	49.20	72952S	4.50	114.3	1.625	41.3	22	3.8	2.4	61	53	235	1.23	31.2	0.156	4.0	7.88	SST	CG	N
1.937	49.20	72964	4.50	114.3	1.613	41.0	28	5.0	3.2	80	90	400	1.34	33.9	0.162	4.1	8.25	MW	CG	N
1.937	49.20	72964S	4.50	114.3	1.613	41.0	24	4.2	2.4	62	59	263	1.34	33.9	0.162	4.1	8.25	SST	CG	N
1.937	49.20	72971	4.50	114.3	1.583	40.2	39	6.8	3.0	76	115	513	1.53	38.8	0.177	4.5	8.63	MW	CG	N
1.937	49.20	72971S	4.50	114.3	1.583	40.2	33	5.8	2.3	59	77	341	1.53	38.8	0.177	4.5	8.63	SST	CG	N
1.937	49.20	72981	4.50	114.3	1.553	39.4	52	9.1	2.8	70	144	642	1.73	43.9	0.192	4.9	9.00	MW	CG	N
1.937	49.20	72981S	4.50	114.3	1.553	39.4	44	7.8	2.0	52	90	402	1.73	43.9	0.192	4.9	9.00	SST	CG	N
1.937	49.20	72989	4.50	114.3	1.523	38.7	72	13	2.6	65	185	823	1.89	48.0	0.207	5.3	9.13	MW	CG	N
1.937	49.20	72989S	4.50	114.3	1.523	38.7	61	11	1.8	47	113	501	1.89	48.0	0.207	5.3	9.13	SST	CG	N
1.937	49.20	73002	4.50	114.3	1.487	37.8	98	17	2.3	59	229	1020	2.14	54.3	0.225	5.7	9.50	MW	CG	N
1.937	49.20	73002S	4.50	114.3	1.487	37.8	84	15	1.6	41	136	603	2.14	54.3	0.225	5.7	9.50	SST	CG	N
1.937	49.20	73013	4.50	114.3	1.437	36.5	148	26	2.0	52	301	1339	2.47	62.7	0.250	6.4	9.88	MW	CG	N
1.937	49.20	73013S	4.50	114.3	1.437	36.5	126	22	1.5	37	184	820	2.47	62.7	0.250	6.4	9.88	SST	CG	N
1.937	49.20	72939	5.00	127.0	1.641	41.7	19	3.3	3.7	95	70	311	1.26	32.0	0.148	3.8	8.50	MW	CG	N
1.937	49.20	72939S	5.00	127.0	1.641	41.7	16	2.8	3.0	75	47	209	1.26	32.0	0.148	3.8	8.50	SST	CG	N
1.937	49.20	72954	5.00	127.0	1.625	41.3	23	4.0	3.6	92	83	371	1.33	33.7	0.156	4.0	8.50	MW	CG	N
1.937	49.20	72954S	5.00	127.0	1.625	41.3	20	3.4	2.7	69	53	235	1.33	33.7	0.156	4.0	8.50	SST	CG	N
1.937	49.20	72965	5.00	127.0	1.613	41.0	25	4.4	3.5	90	90	400	1.46	37.0	0.162	4.1	9.00	MW	MW	CG
1.937	49.20	72965S	5.00	127.0	1.613	41.0	22	3.8	2.7	69	59	263	1.46	37.0	0.162	4.1	9.00	SST	CG	N
1.937	49.20	72972	5.00	127.0	1.583	40.2	35	6.1	3.3	84	115	511	1.68	42.7	0.177	4.5	9.50	MW	CG	N
1.937	49.20	72972S	5.00	127.0	1.583	40.2	29	5.2	2.6	66	77	341	1.68	42.7	0.177	4.5	9.50	SST	CG	N
1.937	49.20	72982	5.00	127.0	1.553	39.4	47	8.1	3.1	79	144	642	1.90	48.2	0.192	4.9	9.88	MW	CG	N
1.937	49.20	72982S	5.00	127.0	1.553	39.4	40	6.9	2.3	58	90	402	1.90	48.2	0.192	4.9	9.88	SST	CG	N
1.937	49.20	72990	5.00	127.0	1.523	38.7	64	11	2.9	73	185	823	2.07	52.6	0.207	5.3	10.0	MW	CG	N
1.937	49.20	72990S	5.00	127.0	1.523	38.7	54	9.5	2.1	53	113	501	2.07	52.6	0.207	5.3	10.0	SST	CG	N
1.937	49.20	73004	5.00	127.0	1.487	37.8	88	15	2.6	67	229	1020	2.33	59.3	0.225	5.7	10.4	MW	CG	N
1.937	49.20	73004S	5.00	127.0	1.487	37.8	74	13	1.8	46	136	603	2.33	59.3	0.225	5.7	10.4	SST	CG	N
1.937	49.20	73014	5.00	127.0	1.437	36.5	132	23	2.3	58	301	1337	2.72	69.1	0.250	6.4	10.9	MW	CG	N
1.937	49.20	73014S	5.00	127.0	1.437	36.5	112	20	1.6	42	184	820	2.72	69.1	0.250	6.4	10.9	SST	CG	N
1.937	49.20	11895	5.25	133.4	1.583	40.2	33	5.8	2.6	66	86	384	1.73	43.8	0.177	4.5	9.75	SPR	CG	N
1.937	49.20	72940	5.50	139.7	1.641	41.7	17	3.0	4.1	105	70	312	1.35	34.3	0.148	3.8	9.13	MW	CG	N
1.937	49.20	72940S	5.50	139.7	1.641	41.7	14	2.5	3.3	83	47	209	1.35	34.3	0.148	3.8	9.13	SST	CG	N
1.937	49.20	72956	5.50	139.7	1.625	41.3	21	3.6	4.0	102	83	371	1.44	36.7	0.156	4.0	9.25	MW	MW	CG
1.937	49.20	72956S	5.50	139.7	1.625	41.3	18	3.1	3.0	76	53	235	1.44	36.7	0.156	4.0	9.25	SST	CG	N
1.937	49.20	72966	5.50	139.7	1.613	41.0	23	4.0	3.9	100	90	399	1.58	40.1	0.162	4.1	9.75	MW	CG	N
1.937	49.20	72966S	5.50	139.7	1.613	41.0	19	3.4	3.0	77	59	263	1.58	40.1	0.162	4.1	9.75	SST	CG	N
1.937	49.20	72973	5.50	139.7	1.583	40.2	31	5.5	3.7	94	115	511	1.81	46.1	0.177	4.5	10.3	MW	CG	N
1.937	49.20	72973S	5.50	139.7	1.583	40.2	27	4.6	2.9	7										



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./in.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
1.953	49.61	S-380	4.13	104.8	1.683	42.7	12	2.2	2.9	73	35	158	1.03	26.1	0.135	3.4	7.67	SST	CG	N
1.953	49.61	11985	4.88	123.8	1.641	41.7	15	2.6	3.0	76	44	196	1.87	47.5	0.156	4.0	12.0	SPR	CG	Z
1.953	49.61	S-3050	5.25	133.4	1.599	40.6	28	4.9	2.7	68	76	339	1.73	43.8	0.177	4.5	9.75	SST	CG	N
1.953	49.61	3375	5.25	133.4	1.329	33.8	385	67	1.0	26	389	1730	3.12	79.2	0.312	7.9	10.0	SPR	CG	Z
1.953	49.61	2687	6.38	161.9	1.599	40.6	19	3.4	3.7	94	72	321	2.66	67.4	0.177	4.5	15.0	HD	CG	Z
1.953	49.61	S-257	6.38	161.9	1.539	39.1	36	6.3	3.1	79	112	497	2.90	73.6	0.207	5.3	14.0	SST	CG	N
1.968	49.99	3376	4.00	101.6	1.594	40.5	104	18	.92	23	96	425	.94	23.7	0.187	4.7	5.00	SPR	CG	Z
1.968	49.99	12626	4.25	108.0	1.698	46.4	12	2.1	3.0	76	35	155	1.05	26.7	.135	3.4	7.75	SST	C	N
1.968	49.99	S-1645	5.50	139.7	1.774	45.1	3.1	.55	4.6	117	14	64	.73	18.5	0.097	2.5	7.50	SST	CG	N
1.968	49.99	4197	8.00	203.2	1.528	38.8	45	7.9	3.3	84	149	661	3.74	95.0	0.225	5.7	16.0	SPR	CG	Z
1.968	49.99	12552	8.00	203.2	1.518	38.6	50	8.7	3.2	81	159	706	3.60	91.4	0.225	5.7	16.0	HD	CG	Z
1.968	49.99	10237	8.00	203.2	1.306	33.2	281	49	1.6	41	458	2037	5.30	134.5	0.331	8.4	16.0	SPR	CG	Z
1.968	49.99	4042	22.0	558.8	1.518	38.6	20	3.6	7.8	197	159	706	8.10	205.7	0.225	5.7	36.0	SPR	CG	Z
1.984	50.39	3170	1.22	31.0	1.756	44.6	15	2.6	.71	18	10	47	.51	13.0	0.114	2.9	4.50	SPR	CG	Z
1.984	50.39	1681	1.25	31.8	1.744	44.3	23	4.0	.77	20	18	79	.48	12.2	0.120	3.0	4.00	SPR	CG	Z
1.984	50.39	S-3071	1.50	38.1	1.774	45.1	15	2.7	1.0	26	16	70	.47	12.0	0.105	2.7	3.50	SST	C	N
1.984	50.39	1875	1.69	42.8	1.704	43.3	88	15	.69	17	61	269	.42	10.7	0.140	3.6	3.00	MW	CG	Z
1.984	50.39	4177	2.88	73.0	1.600	40.6	91	16	1.1	29	103	456	1.10	28.0	0.192	4.9	5.75	SPR	CG	Z
2.000	50.80	S-1243	1.75	44.5	1.550	39.4	229	40	.57	15	132	585	1.01	25.7	0.225	5.7	4.50	SST	CG	N
2.000	50.80	S-120	1.88	47.6	1.616	41.0	144	25	.61	15	88	390	.77	19.5	0.192	4.9	4.00	SST	CG	N
2.000	50.80	11050	2.00	50.8	1.514	38.5	370	65	.53	13	196	871	1.09	27.8	0.243	6.2	4.50	HD	CG	Z
2.000	50.80	11247	2.41	61.1	1.836	46.6	4.6	.81	2.1	53	9.6	43	.33	8.3	0.082	2.1	4.00	MW	CG	N
2.000	50.80	S-365	2.50	63.5	1.876	47.7	.68	.12	2.1	53	1.4	6.3	.42	10.6	0.062	1.6	5.75	SST	C	N
2.000	50.80	11991	2.50	63.5	1.620	41.1	74	13	1.3	33	98	434	1.19	30.2	0.190	4.8	6.25	SPR	CG	Z
2.000	50.80	1795	2.94	74.6	1.730	43.9	23	4.0	1.7	43	39	171	.71	18.0	0.135	3.4	5.25	SPR	CG	Z
2.000	50.80	1673	3.50	88.9	1.550	39.4	125	22	1.2	32	156	695	1.63	41.4	0.225	5.7	7.25	HD	CG	Z
2.000	50.80	S-1650	3.63	92.1	1.828	46.4	1.9	.33	3.0	76	5.7	25	.62	15.8	0.086	2.2	7.25	SST	CG	N
2.000	50.80	S-982	3.63	92.1	1.626	41.3	73	13	1.1	28	81	361	1.03	26.1	0.187	4.7	5.50	SST	CG	N
2.000	50.80	4145	4.00	101.6	1.376	35.0	472	83	.81	20	381	1694	2.50	63.4	0.312	7.9	8.00	SPR	CG	Z
2.000	50.80	S-461	4.50	114.3	1.614	41.0	45	7.9	2.0	50	89	396	1.64	41.7	0.193	4.9	8.50	SST	CG	N
2.000	50.80	S-3113	4.63	117.5	1.676	42.6	17	3.0	3.0	76	52	232	1.62	41.1	0.162	4.1	10.0	SST	CG	N
2.000	50.80	1947	5.09	129.4	1.800	45.7	3.9	.68	4.3	108	17	74	.84	21.3	0.100	2.5	7.38	SPR	C	Z
2.000	50.80	11446	5.63	142.9	1.750	44.5	5.9	1.0	4.1	105	24	109	1.50	38.1	0.125	3.2	11.0	SPR	C	Z
2.000	50.80	3094	6.13	155.6	1.830	46.5	1.5	.27	5.4	136	8.2	36	.77	19.4	0.085	2.2	9.00	SPR	CG	GI
2.000	50.80	3485	6.50	165.1	1.730	43.9	11	2.0	3.4	86	39	171	1.28	32.6	0.135	3.4	8.50	HD	C	GI
2.000	50.80	10441	8.00	203.2	1.550	39.4	51	8.9	3.1	78	156	695	3.38	85.7	0.225	5.7	15.0	SPR	CG	N
2.000	50.80	10247	8.50	215.9	1.434	36.4	152	27	1.9	49	295	1314	3.96	100.6	0.283	7.2	14.0	SPR	CG	GI
2.000	50.80	4239	9.25	235.0	1.550	39.4	41	7.2	3.8	96	156	695	4.05	102.9	0.225	5.7	18.0	SPR	CG	Z
2.000	50.80	3489	9.88	250.8	1.476	37.5	76	13	3.1	79	236	1050	4.98	126.4	0.262	6.7	19.0	SPR	CG	Z
2.000	50.80	S-3198	11.0	279.4	1.768	44.9	3.1	.54	7.5	191	23	103	1.54	39.0	0.116	2.9	13.3	SST	CG	N
2.000	50.80	3124	11.1	282.6	1.750	44.5	5.3	.93	5.9	150	32	140	1.50	38.1	0.125	3.2	12.0	SPR	CG	Z
2.000	50.80	4385	11.8	298.5	1.616	41.0	14	2.5	6.9	174	96	429	4.90	124.4	0.192	4.9	25.5	SPR	CG	Z
2.000	50.80	813	12.0	304.8	1.646	41.8	12	2.1	6.8	174	84	373	3.72	94.4	0.177	4.5	21.0	HD	CG	Z
2.000	50.80	806	12.0	304.8	1.586	40.3	22	3.8	5.9	150	127	565	4.81	122.2	0.207	5.3	23.3	HD	CG	Z
2.000	50.80	837	12.0	304.8	1.550	39.4	30	5.2	5.2	133	156	695	5.40	137.2	0.225	5.7	24.0	HD	CG	Z
2.000	50.80	676	12.0	304.8	1.376	35.0	142	25	2.7	68	381	1694	6.86	174.3	0.312	7.9	22.0	SPR	CG	Z
2.015	51.18	S-1665	2.34	59.5	1.565	39.8	175	31	.75	19	131	581	1.18	30.0	0.225	5.7	5.25	SST	CG	N
2.015	51.18	S-1664	2.44	61.9	1.565	39.8	190	33	.69	17	131	581	1.13	28.6	0.225	5.7	5.00	SST	CG	N
2.015	51.18	11975	3.41	86.5	1.745	44.3	14	2.5	2.5	63	35	157	.95	24.0	0.135	3.4	7.00	SPR	CG	Z
2.031	51.59	S-3196	4.66	118.3	1.873	47.6	1.3	.23	4.0	102	5.4	24	.63	16.1	0.079	2.0	7.00	SST	C	N
2.031	51.59	3413	5.25	133.4	1.847	46.9	2.0	.35	4.3	110	8.7	39	.92	23.4	0.092	2.3	9.00	SPR	C	Z
2.031	51.59	4353	6.75	171.5	1.465	37.2	145	25	2.0	51	291	1296	3.79	96.4	0.283	7.2	13.5	SPR	CG	Z
2.046	51.97	11931	1.53	38.9	1.794	45.6	20	3.6	.96	24	20	88	.57	14.4	0.126	3.2	4.50	SPR	CG	Z
2.046	51.97	10651	2.53	64.3	1.522	38.7	434	76	.53	14	231	1028	1.25	31.6	0.262	6.7	4.75	SPR	CG	Z
2.046	51.97	3379	3.13	79.4	1.692	43.0	43	7.6	1.9	48	82	363	1.24	31.5	0.177	4.5	7.00	SPR	CG	GI
2.046	51.97	S-1619	3.75	95.3	1.924	48.9	.75	.13	3.4	88	2.6	12								



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
2.078	52.78	S-1661	4.44	112.7	1.870	47.5	4.3	.75	3.8	96	16	72	.68	17.2	0.104	2.6	6.50	SST	CG	N
2.094	53.19	3372	1.38	34.9	1.644	41.8	564	99	.27	6.7	150	666	.68	17.1	0.225	5.7	3.00	SPR	CG	Z
2.094	53.19	11715	1.75	44.5	1.956	49.7	1.3	.23	1.4	36	1.8	8.2	.35	8.8	0.069	1.8	5.00	SPR	CG	GI
2.094	53.19	4298	2.25	57.2	1.854	47.1	14	2.5	1.7	43	24	105	.57	14.5	0.120	3.0	4.75	SPR	CG	Z
2.094	53.19	11869	2.53	64.3	1.782	45.3	19	3.3	1.4	35	26	114	1.17	29.7	0.156	4.0	7.50	SST	CG	N
2.094	53.19	10400	4.50	114.3	1.798	45.7	17	3.0	2.8	72	48	215	1.11	28.2	0.148	3.8	7.50	SPR	CG	Z
2.109	53.57	3229	1.06	27.0	1.721	43.7	193	34	.38	9.7	74	329	.68	17.2	0.194	4.9	3.50	SPR	CG	Z
2.109	53.57	S-389	1.38	34.9	1.585	40.3	703	123	.26	6.7	186	826	.89	22.6	0.262	6.7	3.38	SST	CG	N
2.109	53.57	2754	1.50	38.1	1.869	47.5	38	6.6	.98	25	37	165	.36	9.1	0.120	3.0	3.00	MW	CG	Z
2.109	53.57	12083	1.66	42.1	1.899	48.2	14	2.5	1.3	32	18	82	.37	9.3	0.105	2.7	3.50	SPR	CG	Z
2.109	53.57	S-1644	2.06	52.4	1.785	45.3	28	4.9	1.0	27	29	131	1.01	25.7	0.162	4.1	6.25	SST	CG	N
2.109	53.57	3452	2.25	57.2	1.925	48.9	4.2	.73	1.8	45	7.5	33	.46	11.7	0.092	2.3	5.00	SPR	CG	Z
2.109	53.57	S-1674	2.50	63.5	1.989	50.5	.55	.10	2.1	54	1.2	5.2	.39	9.9	0.060	1.5	5.50	SST	C	N
2.109	53.57	2688	2.88	73.0	1.705	43.3	86	15	1.3	33	112	500	1.21	30.8	0.202	5.1	6.00	SPR	CG	Z
2.109	53.57	1615	2.91	73.8	1.321	33.6	1962	344	.35	8.8	677	3012	2.17	55.0	0.394	10.0	5.50	SPR	CG	Z
2.109	53.57	11849	4.63	117.5	1.917	48.7	3.8	.66	3.4	88	13	58	.62	15.8	0.096	2.4	5.50	SST	C	N
2.109	53.57	S-152	4.84	123.0	1.927	48.9	2.6	.46	4.3	109	11	50	.55	13.9	0.091	2.3	6.00	SST	CG	N
2.109	53.57	S-3023	5.50	139.7	1.749	44.4	17	3.0	3.3	83	57	252	2.25	57.2	0.180	4.6	12.5	SST	CG	N
2.109	53.57	S-3236	6.03	153.2	1.899	48.2	3.8	.66	4.5	115	17	76	.81	20.7	0.105	2.7	7.75	SST	CG	N
2.109	53.57	12627	8.50	215.9	1.649	41.9	56	9.9	2.8	71	159	706	2.93	74.5	0.230	5.8	12.8	SPR	CG	N
2.125	53.98	S-3151	.69	17.4	1.875	47.6	76	13	.25	6.3	19	85	.44	11.1	0.125	3.2	2.50	SST	C	N
2.125	53.98	S-3072	3.63	92.1	1.813	46.1	16	2.8	2.4	60	38	171	1.25	31.7	0.156	4.0	8.00	SST	CG	N
2.125	53.98	10607	5.38	136.5	1.915	48.6	2.1	.37	4.1	105	8.6	38	1.26	32.0	0.105	2.7	11.0	SST	C	N
2.125	53.98	11860	5.38	136.5	1.899	48.2	5.5	.96	4.0	102	22	98	.93	23.7	0.113	2.9	7.25	SPR	C	N
2.125	53.98	S-3168	5.50	139.7	1.899	48.2	5.0	.88	4.0	102	20	89	.79	20.1	0.113	2.9	7.00	SST	CG	N
2.125	53.98	S-3213	5.66	143.7	1.859	47.2	6.1	1.1	4.3	109	26	117	1.36	34.6	0.133	3.4	10.3	SST	CG	N
2.125	53.98	12054	6.03	153.2	1.915	48.6	3.3	.57	5.2	132	17	75	.81	20.7	0.105	2.7	7.75	SST	CG	N
2.125	53.98	4332	6.50	165.1	1.511	38.4	202	35	1.7	43	344	1531	3.84	97.5	0.307	7.8	12.5	SPR	CG	Z
2.125	53.98	S-1640	6.75	171.5	1.813	46.1	13	2.3	3.7	93	48	215	1.48	37.6	0.156	4.0	9.50	SST	CG	N
2.125	53.98	S-3093	7.00	177.8	1.941	49.3	2.8	.50	4.0	102	11	51	.62	15.8	0.092	2.3	5.75	SST	C	N
2.125	53.98	S-3161	7.00	177.8	1.855	47.1	7.0	1.2	4.7	118	33	145	1.42	36.0	0.135	3.4	9.50	SST	C	N
2.140	54.36	S-3211	2.34	59.5	1.984	50.4	1.7	.29	1.9	49	3.2	14	.41	10.4	0.078	2.0	5.25	SST	CG	N
2.140	54.36	S-89	2.63	66.7	1.700	43.2	83	14	1.1	28	90	399	1.54	39.1	0.220	5.6	7.00	SST	CG	N
2.140	54.36	S-101	3.13	79.4	1.828	46.4	31	5.4	1.6	40	48	213	.78	19.7	0.156	4.0	5.00	SST	CG	N
2.140	54.36	S-3073	3.25	82.6	1.766	44.9	34	6.0	1.8	45	60	267	1.50	38.0	0.187	4.7	8.00	SST	CG	N
2.140	54.36	11604	3.50	88.9	2.006	51.0	.81	.14	3.0	77	2.5	11	.47	11.9	0.067	1.7	6.00	SPR	CG	Z
2.140	54.36	S-174	4.38	111.1	1.920	48.8	6.3	1.1	2.9	75	18	82	.61	15.4	0.110	2.8	5.50	SST	CG	N
2.140	54.36	S-447	5.16	131.0	1.930	49.0	6.0	1.1	2.8	71	17	75	.53	13.3	0.105	2.7	5.00	SST	C	N
2.140	54.36	1841	5.75	146.1	1.936	49.2	3.7	.64	4.9	125	18	81	.82	20.7	0.102	2.6	7.00	MW	C	Z
2.140	54.36	S-258	6.38	161.9	1.890	48.0	4.1	.73	5.0	127	21	92	1.38	34.9	0.125	3.2	11.0	SST	CG	N
2.140	54.36	S-3019	8.88	225.4	1.780	45.2	15	2.5	4.7	119	68	302	2.52	64.0	0.180	4.6	14.0	SST	CG	N
2.140	54.36	4101	9.00	228.6	1.516	38.5	127	22	2.8	71	359	1595	6.08	154.5	0.312	7.9	19.5	SPR	CG	Z
2.156	54.76	11786	1.47	37.3	2.000	50.8	4.0	.69	1.2	30	4.7	21	.27	6.9	0.078	2.0	3.50	SPR	CG	N
2.156	54.76	S-3036	5.50	139.7	1.886	47.9	6.3	1.1	4.2	105	26	116	1.35	34.3	0.135	3.4	10.0	SST	CG	N
2.172	55.17	11823	5.75	146.1	1.962	49.8	3.5	.61	4.7	120	17	74	.74	18.7	0.105	2.7	7.00	SST	CG	N
2.187	55.55	3493	1.75	44.5	1.927	48.9	16	2.8	1.1	28	17	77	.65	16.5	0.130	3.3	5.00	SPR	CG	Z
2.187	55.55	3059	2.13	54.0	1.917	48.7	26	4.6	1.4	34	35	157	.56	14.1	0.135	3.4	4.00	SPR	CG	GI
2.187	55.55	73017	4.00	101.6	1.773	45.0	68	12	1.9	49	131	584	1.45	36.8	0.207	5.3	7.00	OT	CG	N
2.187	55.55	73024	4.00	101.6	1.751	44.5	81	14	1.9	48	153	680	1.58	40.2	0.218	5.5	7.25	OT	CG	N
2.187	55.55	73031	4.00	101.6	1.687	42.8	134	24	1.6	42	220	980	1.94	49.2	0.250	6.4	7.75	OT	CG	N
2.187	55.55	73038	4.00	101.6	1.625	41.3	216	38	1.4	35	300	1335	2.25	57.1	0.281	7.1	8.00	OT	CG	N
2.187	55.55	73045	4.00	101.6	1.563	39.7	344	60	1.1	29	396	1759	2.50	63.4	0.312	7.9	8.00	OT	CG	N
2.187	55.55	73052	4.00	101.6	1.501	38.1	552	97	.92	23	508	2261	2.66	67.5	0.343	8.7	7.75	OT	CG	N
2.187	55.55	73059	4.00	101.6	1.437	36.5	831	146	.79	20	657	2922	2.91	73.8	0.375	9.5	7.75	OT	CG	N
2.187	55.55	73066	4.00	101.6	1.401	35.6	1080	189	.68	17	733	3262	2.95	74.9	0.393	10.0	7.50	OT	CG	N
2.187	55.55	S-1641	4.09	104.0	1.813	46.1	41	7.2	1.8</											



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	FNSH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
2.187	55.55	73048	7.00	177.8	1.563	39.7	183	32	2.2	55	396	1759	4.15	105.4	0.312	7.9	13.3	OT	CG	N
2.187	55.55	73055	7.00	177.8	1.501	38.1	289	51	1.8	45	508	2261	4.46	113.2	0.343	8.7	13.0	OT	CG	N
2.187	55.55	73062	7.00	177.8	1.437	36.5	432	76	1.5	39	657	2922	4.90	124.4	0.375	9.5	13.1	OT	CG	N
2.187	55.55	73069	7.00	177.8	1.401	35.6	559	98	1.3	33	733	3262	4.96	126.0	0.393	10.0	12.6	OT	CG	N
2.187	55.55	73021	8.00	203.2	1.773	45.0	32	5.7	4.1	103	131	584	2.59	65.9	0.207	5.3	12.5	OT	CG	N
2.187	55.55	73028	8.00	203.2	1.751	44.5	38	6.6	4.0	103	153	680	2.89	73.4	0.218	5.5	13.3	OT	CG	N
2.187	55.55	73035	8.00	203.2	1.687	42.8	62	11	3.6	91	220	980	3.63	92.1	0.250	6.4	14.5	OT	CG	N
2.187	55.55	73042	8.00	203.2	1.625	41.3	100	17	3.0	77	300	1335	4.21	107.0	0.281	7.1	15.0	OT	CG	N
2.187	55.55	73049	8.00	203.2	1.563	39.7	157	28	2.5	64	396	1759	4.72	119.9	0.312	7.9	15.1	OT	CG	N
2.187	55.55	73056	8.00	203.2	1.501	38.1	249	44	2.0	52	508	2261	5.06	128.5	0.343	8.7	14.7	OT	CG	N
2.187	55.55	73063	8.00	203.2	1.437	36.5	372	65	1.8	45	657	2922	5.57	141.5	0.375	9.5	14.9	OT	CG	N
2.187	55.55	73070	8.00	203.2	1.401	35.6	480	84	1.5	39	733	3262	5.65	143.5	0.393	10.0	14.4	OT	CG	N
2.187	55.55	73022	9.00	228.6	1.773	45.0	28	5.0	4.6	118	131	584	2.90	73.7	0.207	5.3	14.0	OT	CG	N
2.187	55.55	73029	9.00	228.6	1.751	44.5	33	5.8	4.6	117	153	680	3.22	81.8	0.218	5.5	14.8	OT	CG	N
2.187	55.55	73036	9.00	228.6	1.687	42.8	55	9.7	4.0	101	220	980	4.00	101.6	0.250	6.4	16.0	OT	CG	N
2.187	55.55	73043	9.00	228.6	1.625	41.3	88	15	3.4	87	300	1335	4.70	119.5	0.281	7.1	16.7	OT	CG	N
2.187	55.55	73050	9.00	228.6	1.563	39.7	139	24	2.8	72	396	1759	5.27	133.7	0.312	7.9	16.9	OT	CG	N
2.187	55.55	73057	9.00	228.6	1.501	38.1	219	38	2.3	59	508	2261	5.66	143.8	0.343	8.7	16.5	OT	CG	N
2.187	55.55	73064	9.00	228.6	1.437	36.5	327	57	2.0	51	657	2922	6.23	158.4	0.375	9.5	16.6	OT	CG	N
2.187	55.55	73071	9.00	228.6	1.401	35.6	422	74	1.7	44	733	3262	6.32	160.4	0.393	10.0	16.1	OT	CG	N
2.187	55.55	73023	10.0	254.0	1.773	45.0	26	4.5	5.1	130	131	584	3.16	80.3	0.207	5.3	15.3	OT	CG	N
2.187	55.55	73030	10.0	254.0	1.751	44.5	30	5.2	5.1	130	153	680	3.55	90.1	0.218	5.5	16.3	OT	CG	N
2.187	55.55	73037	10.0	254.0	1.687	42.8	50	8.7	4.4	112	220	980	4.38	111.2	0.250	6.4	17.5	OT	CG	N
2.187	55.55	73044	10.0	254.0	1.625	41.3	78	14	3.8	97	300	1335	5.20	132.1	0.281	7.1	18.5	OT	CG	N
2.187	55.55	73051	10.0	254.0	1.563	39.7	124	22	3.2	81	396	1759	5.81	147.6	0.312	7.9	18.6	OT	CG	N
2.187	55.55	73058	10.0	254.0	1.501	38.1	195	34	2.6	66	508	2261	6.26	159.0	0.343	8.7	18.2	OT	CG	N
2.187	55.55	73065	10.0	254.0	1.437	36.5	292	51	2.3	57	657	2922	6.89	175.0	0.375	9.5	18.4	OT	CG	N
2.187	55.55	73072	10.0	254.0	1.401	35.6	376	66	2.0	50	733	3262	7.00	177.7	0.393	10.0	17.8	OT	CG	N
2.203	55.96	4276	5.00	127.0	1.933	49.1	10	1.8	3.4	87	35	156	.98	24.9	0.135	3.4	7.25	SPR	CG	Z
2.219	56.36	3072	1.38	34.9	1.695	43.1	904	158	.24	6.0	214	954	.79	20.0	0.262	6.7	3.00	SPR	CG	Z
2.219	56.36	12615	1.75	44.5	2.035	51.7	4.7	.81	1.3	33	6.0	27	.46	11.7	0.092	2.3	4.00	SST	C	N
2.219	56.36	11297	3.75	95.3	1.907	48.4	24	4.2	2.2	55	52	232	.94	23.8	0.156	4.0	6.00	SPR	CG	Z
2.219	56.36	4227	5.75	146.1	1.949	49.5	10	1.8	3.5	88	35	155	.98	24.9	0.135	3.4	7.25	SPR	CG	Z
2.234	56.74	3205	5.00	127.0	1.820	46.2	47	8.2	2.4	62	114	509	1.81	46.0	0.207	5.3	8.75	SPR	CG	Z
2.250	57.15	S-3219	2.09	53.2	1.954	49.6	15	2.7	1.2	30	18	81	.93	23.5	0.148	3.8	6.25	SST	CG	N
2.250	57.15	S-3215	3.25	82.6	2.040	51.8	6.3	1.1	2.6	65	16	71	.47	12.0	0.105	2.7	4.50	SST	CG	N
2.250	57.15	4394	5.25	133.4	1.750	44.5	134	23	1.4	36	191	848	1.81	46.0	0.250	6.4	7.25	SPR	CG	Z
2.250	57.15	4366	5.75	146.1	1.374	34.9	1046	183	.81	21	845	3759	4.60	116.8	0.438	11.1	10.5	SPR	CG	N
2.250	57.15	4218	7.00	177.8	1.926	48.9	15	2.6	3.8	98	58	256	1.50	38.1	0.162	4.1	9.25	SPR	CG	N
2.250	57.15	S-355	7.50	190.5	1.980	50.3	4.1	.71	5.6	143	23	102	1.86	47.1	0.135	3.4	12.8	SST	C	N
2.250	57.15	1935	8.13	206.4	1.836	46.6	31	5.4	3.7	93	114	505	2.48	63.1	0.207	5.3	12.0	SPR	CG	Z
2.250	57.15	S-354	9.25	235.0	2.010	51.1	2.2	.39	7.6	192	17	75	1.68	42.7	0.120	3.0	14.0	SST	CG	N
2.250	57.15	10161	9.50	241.3	1.726	43.8	72	13	2.9	75	212	942	3.67	93.2	0.262	6.7	14.0	SPR	CG	N
2.250	57.15	10275	9.50	241.3	1.684	42.8	105	18	2.5	64	265	1180	3.82	97.1	0.283	7.2	13.5	SPR	CG	Z
2.250	57.15	7013	10.0	254.0	1.500	38.1	250	44	2.3	58	570	2534	7.70	195.6	0.375	9.5	19.3	HD	C	Z
2.250	57.15	10692	14.0	355.6	1.876	47.7	9.0	1.6	9.3	236	83	371	4.72	119.9	0.187	4.7	24.3	SPR	C	Z
2.250	57.15	7015	16.0	406.4	1.500	38.1	150	26	3.8	96	570	2534	12.0	304.8	0.375	9.5	30.8	HD	C	Z
2.266	57.56	S-1660	2.78	70.6	1.832	46.5	110	19	1.0	26	112	497	1.09	27.6	0.217	5.5	5.00	SST	CG	N
2.281	57.94	S-1646	1.38	34.9	1.987	50.5	46	8.1	.85	22	39	175	.49	12.4	0.147	3.7	3.33	SST	CG	N
2.281	57.94	10272	9.50	241.3	1.715	43.6	108	19	2.4	62	262	1165	3.61	91.6	0.283	7.2	12.8	SPR	CG	Z
2.296	58.32	10984	1.94	49.2	1.796	45.6	219	38	.69	17	150	669	1.25	31.8	0.250	6.4	5.00	HD	CG	N
2.296	58.32	S-1629	8.09	205.6	2.058	52.3	3.3	.58	6.6	167	22	97	1.13	28.7	0.119	3.0	9.50	SST	CG	N
2.296	58.32	S-1659	10.4	263.5	2.058	52.3	3.1	.54	7.0	178	22	97	1.19	30.2	0.119	3.0	10.0	SST	CG	N
2.312	58.72	12082	1.97	50.0	2.188	55.6	.47	.08	1.5	39	.72	3.2	.43	11.0	0.062	1.6	6.00	SPR	C	Z
2.312	58.72	4198	3.00	76.2	2.122	53.9	2.1	.38	2.2	57	4.8	21	.76	19.3	0.095	2.4	7.00	SPR	C	Z
2.312	58.72	4354	3.25	82.6	1.588	40.3														



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E NDS	FINISH
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
2.375	60.33	S-318	5.75	146.1	2.165	55.0	2.7	.48	5.0	128	14	61	.71	18.0	0.105	2.7	6.75	SST	CG	N
2.375	60.33	S-3094	6.63	168.3	2.063	52.4	14	2.4	3.2	82	43	193	1.04	26.4	0.156	4.0	6.75	SST	CG	N
2.375	60.33	4326	7.50	190.5	2.051	52.1	12	2.1	4.5	114	55	243	1.54	39.1	0.162	4.1	9.50	SPR	CG	Z
2.375	60.33	12043	9.56	242.9	2.079	52.8	6.9	1.2	6.2	157	43	191	1.63	41.4	0.148	3.8	11.0	SPR	CG	Z
2.375	60.33	S-137	11.8	298.5	2.063	52.4	5.4	.95	8.0	203	43	193	2.26	57.5	0.156	4.0	14.5	SST	CG	N
2.375	60.33	4405	11.8	298.5	1.751	44.5	113	20	2.9	73	326	1451	4.91	124.8	0.312	7.9	15.8	SPR	CG	Z
2.390	60.71	4168	3.13	79.4	2.036	51.7	43	7.6	1.6	41	71	314	.89	22.5	0.177	4.5	5.00	SPR	CG	Z
2.406	61.11	S-149	2.13	54.0	2.110	53.6	19	3.3	1.4	37	27	122	.69	17.4	0.148	3.8	4.67	SST	CG	N
2.406	61.11	11573	3.06	77.8	2.242	56.9	3.5	.60	2.3	59	8.1	36	.37	9.4	0.082	2.1	3.50	SPR	C	N
2.406	61.11	4112	3.13	79.4	2.052	52.1	42	7.4	1.7	42	70	312	.89	22.5	0.177	4.5	5.00	SPR	CG	Z
2.406	61.11	S-986	3.16	80.2	1.992	50.6	65	11	1.4	36	92	408	1.10	28.0	0.207	5.3	5.33	SST	CG	N
2.406	61.11	10582	3.75	95.3	1.882	47.8	161	28	1.3	33	206	914	1.64	41.6	0.262	6.7	6.3	SPR	CG	N
2.406	61.11	10278	4.00	101.6	1.882	47.8	153	27	1.3	33	199	884	1.70	43.3	0.262	6.7	6.50	SPR	CG	N
2.406	61.11	S-161	4.13	104.8	2.094	53.2	11	1.9	2.9	73	31	139	1.25	31.7	0.156	4.0	8.00	SST	CG	N
2.406	61.11	S-964	4.88	123.8	2.196	55.8	3.1	.55	4.1	105	13	57	.74	18.7	0.105	2.7	6.00	SST	C	N
2.406	61.11	11506	5.13	130.2	1.972	50.1	51	8.9	2.4	61	122	545	1.95	49.6	0.217	5.5	8.00	SPR	CG	Z
2.406	61.11	S-396	7.00	177.8	2.166	55.0	3.7	.65	5.8	146	21	95	.95	24.0	0.120	3.0	8.00	SST	CG	N
2.406	61.11	S-3098	16.0	406.4	2.094	53.2	5.9	1.0	7.2	183	43	191	2.08	52.8	0.156	4.0	13.3	SST	CG	N
2.421	61.49	10276	3.00	76.2	1.855	47.1	252	44	.99	25	248	1102	1.63	41.3	0.283	7.2	5.75	SPR	CG	N
2.437	61.90	4203	3.00	76.2	2.083	52.9	41	7.1	1.7	43	69	308	.89	22.5	0.177	4.5	5.00	SPR	CG	Z
2.437	61.90	73073	4.00	101.6	1.875	47.6	170	30	1.6	41	271	1207	2.04	51.8	0.281	7.1	7.26	OT	CG	N
2.437	61.90	73079	4.00	101.6	1.813	46.1	270	47	1.3	34	358	1594	2.26	57.5	0.312	7.9	7.26	OT	CG	N
2.437	61.90	73085	4.00	101.6	1.751	44.5	412	72	1.1	28	461	2052	2.49	63.3	0.343	8.7	7.26	OT	CG	N
2.437	61.90	73091	4.00	101.6	1.713	43.5	526	92	1.0	26	539	2399	2.63	66.7	0.362	9.2	7.25	OT	CG	N
2.437	61.90	73097	4.00	101.6	1.687	42.8	617	108	.97	25	597	2657	2.72	69.1	0.375	9.5	7.26	OT	CG	N
2.437	61.90	73103	4.00	101.6	1.651	41.9	765	134	.87	22	668	2970	2.85	72.4	0.393	10.0	7.25	OT	CG	N
2.437	61.90	73109	4.00	101.6	1.625	41.3	932	163	.79	20	733	3261	2.84	72.2	0.406	10.3	7.00	OT	CG	N
2.437	61.90	73115	4.00	101.6	1.563	39.7	1310	229	.67	17	883	3929	3.06	77.7	0.437	11.1	7.00	OT	CG	N
2.437	61.90	73074	5.00	127.0	1.875	47.6	132	23	2.1	52	271	1207	2.47	62.6	0.281	7.1	8.78	OT	CG	N
2.437	61.90	73080	5.00	127.0	1.813	46.1	210	37	1.7	43	358	1594	2.73	69.4	0.312	7.9	8.76	OT	CG	N
2.437	61.90	73086	5.00	127.0	1.751	44.5	315	55	1.5	37	461	2052	3.05	77.4	0.343	8.7	8.88	OT	CG	N
2.437	61.90	73092	5.00	127.0	1.713	43.5	402	70	1.3	34	539	2399	3.21	81.6	0.362	9.2	8.87	OT	CG	N
2.437	61.90	73098	5.00	127.0	1.687	42.8	472	83	1.3	32	597	2657	3.33	84.5	0.375	9.5	8.87	OT	CG	N
2.437	61.90	73104	5.00	127.0	1.651	41.9	584	102	1.1	29	668	2970	3.49	88.6	0.393	10.0	8.88	OT	CG	N
2.437	61.90	73110	5.00	127.0	1.625	41.3	704	123	1.0	26	733	3261	3.50	88.9	0.406	10.3	8.62	OT	CG	N
2.437	61.90	73116	5.00	127.0	1.563	39.7	989	173	.89	23	883	3929	3.77	95.7	0.437	11.1	8.63	OT	CG	



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	END S	F.N.S.H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
2.500	63.50	10286	6.50	165.1	1.812	46.0	259	45	1.6	40	404	1797	3.35	85.2	0.344	8.7	9.75	SPR	CG	Z
2.500	63.50	10238	7.75	196.9	1.888	48.0	140	25	2.1	53	294	1307	3.21	81.6	0.306	7.8	10.5	SPR	CG	N
2.500	63.50	10310	9.63	244.5	1.776	45.1	235	41	2.0	51	469	2084	4.62	117.2	0.362	9.2	12.8	SPR	CG	N
2.500	63.50	S-1639	10.5	266.7	2.030	51.6	20	3.6	6.0	152	121	539	4.35	110.4	0.235	6.0	18.5	SST	CG	N
2.500	63.50	S-3082	17.0	431.8	2.188	55.6	2.6	.45	13	332	34	149	3.93	99.7	0.156	4.0	25.0	SST	CG	N
2.562	65.07	S-1651	1.94	49.2	2.178	55.3	43	7.6	.98	25	42	189	.96	24.4	0.192	4.9	5.00	SST	CG	N
2.578	65.48	3391	3.50	88.9	1.888	48.0	457	80	.87	22	396	1762	2.07	52.6	0.345	8.8	6.00	SPR	CG	Z
2.593	65.86	S-410	8.75	222.3	2.383	60.5	2.0	.35	7.1	180	14	62	.74	18.7	0.105	2.7	7.00	SST	CG	N
2.593	65.86	11896	9.63	244.5	2.123	53.9	30	5.3	4.6	116	139	618	3.06	77.6	0.235	6.0	13.0	SPR	CG	N
2.625	66.68	11969	2.84	72.2	2.191	55.7	91	16	1.2	31	113	501	.98	24.8	0.217	5.5	4.50	SPR	CG	Z
2.625	66.68	S-980	3.00	76.2	2.445	62.1	1.9	.34	2.5	63	4.8	21	.51	12.9	0.090	2.3	4.67	SST	C	N
2.625	66.68	S-418	3.00	76.2	2.433	61.8	3.3	.57	2.5	64	8.3	37	.48	12.2	0.096	2.4	4.00	SST	C	N
2.625	66.68	S-993	3.88	98.4	2.097	53.3	95	17	1.6	42	155	688	1.82	46.1	0.264	6.7	7.00	SST	CG	N
2.625	66.68	4410	4.00	101.6	1.749	44.4	1012	177	.82	21	834	3709	3.07	77.9	0.438	11.1	7.00	OT	CG	N
2.687	68.25	4135	2.50	63.5	2.437	61.9	12	2.0	2.0	50	23	102	.51	13.0	0.125	3.2	4.00	SPR	CG	Z
2.687	68.25	73121	4.00	101.6	2.063	52.4	226	40	1.4	37	327	1456	2.03	51.5	0.312	7.9	6.50	OT	CG	N
2.687	68.25	73128	4.00	101.6	2.001	50.8	343	60	1.2	31	422	1877	2.23	56.6	0.343	8.7	6.50	OT	CG	N
2.687	68.25	73135	4.00	101.6	1.963	49.9	437	76	1.1	29	494	2196	2.35	59.8	0.362	9.2	6.50	OT	CG	N
2.687	68.25	73142	4.00	101.6	1.937	49.2	511	90	1.1	27	547	2434	2.44	61.9	0.375	9.5	6.50	OT	CG	N
2.687	68.25	73149	4.00	101.6	1.901	48.3	631	111	.97	25	612	2723	2.55	64.9	0.393	10.0	6.50	OT	CG	N
2.687	68.25	73156	4.50	114.3	1.875	47.6	627	110	1.1	27	673	2992	2.94	74.8	0.406	10.3	7.25	OT	CG	N
2.687	68.25	73163	4.50	114.3	1.813	46.1	877	154	.93	24	812	3610	3.17	80.5	0.437	11.1	7.25	OT	CG	N
2.687	68.25	73170	4.50	114.3	1.751	44.5	1262	221	.78	20	988	4395	3.28	83.2	0.468	11.9	7.00	OT	CG	N
2.687	68.25	3327	4.88	123.8	2.313	58.8	16	2.8	3.2	81	51	228	1.68	42.7	0.187	4.7	9.00	SPR	CG	Z
2.687	68.25	73122	5.00	127.0	2.063	52.4	175	31	1.9	47	327	1456	2.43	61.8	0.312	7.9	7.80	OT	CG	N
2.687	68.25	73129	5.00	127.0	2.001	50.8	262	46	1.6	41	422	1877	2.71	68.8	0.343	8.7	7.90	OT	CG	N
2.687	68.25	73136	5.00	127.0	1.963	49.9	334	59	1.5	38	494	2196	2.85	72.4	0.362	9.2	7.88	OT	CG	N
2.687	68.25	73143	5.00	127.0	1.937	49.2	392	69	1.4	35	547	2434	2.95	75.0	0.375	9.5	7.88	OT	CG	N
2.687	68.25	73150	5.00	127.0	1.901	48.3	481	84	1.3	32	612	2723	3.11	78.9	0.393	10.0	7.90	OT	CG	N
2.687	68.25	73157	5.00	127.0	1.875	47.6	549	96	1.2	31	673	2992	3.25	82.5	0.406	10.3	8.00	OT	CG	N
2.687	68.25	73164	5.00	127.0	1.813	46.1	767	134	1.1	27	812	3610	3.50	88.8	0.437	11.1	8.00	OT	CG	N
2.687	68.25	73171	5.00	127.0	1.751	44.5	1107	194	.89	23	988	4395	3.60	91.5	0.468	11.9	7.70	OT	CG	N
2.687	68.25	73123	6.00	152.4	2.063	52.4	143	25	2.3	58	327	1456	2.85	72.4	0.312	7.9	9.13	OT	CG	N
2.687	68.25	73130	6.00	152.4	2.001	50.8	213	37	2.0	50	422	1877	3.17	80.6	0.343	8.7	9.25	OT	CG	N
2.687	68.25	73137	6.00	152.4	1.963	49.9	271	47	1.8	46	494	2196	3.35	85.0	0.362	9.2	9.25	OT	CG	N
2.687	68.25	73144	6.00	152.4	1.937	49.2	317	56	1.7	44	547	2434	3.47	88.1	0.375	9.5				




O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
2.750	69.85	4336	4.75	120.7	2.300	58.4	65	11	1.8	45	116	514	1.24	31.4	0.225	5.7	5.50	SPR	CG	Z
2.750	69.85	4086	6.25	158.8	2.000	50.8	303	53	1.6	40	476	2118	3.38	85.7	0.375	9.5	9.00	HD	CG	N
2.750	69.85	4093	8.50	215.9	1.250	31.8	7107	1245	.36	9.2	2563	11400	7.50	190.5	0.750	19.1	10.0	HD	CG	N
2.750	69.85	S-3116	14.0	355.6	2.438	61.9	6.1	1.1	6.2	158	38	167	1.40	35.7	0.156	4.0	9.00	SST	CG	N
2.796	71.02	11890	9.00	228.6	2.564	65.1	1.5	.27	7.8	197	12	53	1.25	31.7	0.116	2.9	9.75	SST	C	N
2.812	71.42	4328	1.63	41.3	1.938	49.2	3913	685	.18	4.5	693	3082	1.31	33.3	0.437	11.1	3.00	SPR	CG	Z
2.812	71.42	4334	13.0	330.2	2.246	57.0	33	5.7	6.6	168	215	958	5.52	140.2	0.283	7.2	19.5	SPR	CG	Z
2.875	73.03	S-3095	2.88	73.0	2.351	59.7	189	33	.74	19	139	617	.98	25.0	0.262	6.7	3.75	SST	CG	N
2.875	73.03	S-3159	3.00	76.2	2.625	66.7	15	2.6	1.4	35	20	90	.50	12.7	0.125	3.2	3.00	SST	C	N
2.875	73.03	S-86	3.00	76.2	2.491	63.3	39	6.8	1.6	40	62	275	.82	20.7	0.192	4.9	4.25	SST	CG	N
2.875	73.03	S-995	3.63	92.1	2.309	58.6	107	19	1.6	41	174	775	1.76	44.6	0.283	7.2	6.25	SST	CG	N
2.875	73.03	4240	6.75	171.5	2.087	53.0	378	66	1.4	35	516	2293	3.15	80.1	0.394	10.0	8.00	SPR	CG	Z
2.875	73.03	4314	7.50	190.5	2.375	60.3	52	9.1	2.9	74	151	673	2.00	50.8	0.250	6.4	8.00	SPR	CG	Z
2.875	73.03	S-3124	8.50	215.9	2.375	60.3	39	6.8	3.3	84	127	566	2.25	57.2	0.250	6.4	9.00	SST	CG	N
2.875	73.03	11314	12.8	323.9	2.213	56.2	71	12	4.6	116	325	1445	5.54	140.8	0.331	8.4	16.8	SPR	CG	N
2.906	73.81	3313	1.50	38.1	2.492	63.3	135	24	.66	17	89	395	.62	15.8	0.207	5.3	3.00	SPR	CG	Z
2.906	73.81	73177	4.00	101.6	2.344	59.5	116	20	2.0	50	230	1023	1.76	44.8	0.281	7.1	6.27	OT	CG	N
2.906	73.81	73183	4.00	101.6	2.282	58.0	184	32	1.7	42	304	1353	1.95	49.5	0.312	7.9	6.24	OT	CG	N
2.906	73.81	73189	4.00	101.6	2.220	56.4	278	49	1.4	36	392	1746	2.14	54.5	0.343	8.7	6.25	OT	CG	N
2.906	73.81	73195	4.00	101.6	2.182	55.4	352	62	1.3	33	459	2044	2.27	57.6	0.362	9.2	6.26	OT	CG	N
2.906	73.81	73201	4.00	101.6	2.156	54.8	412	72	1.2	31	509	2266	2.35	59.6	0.375	9.5	6.26	OT	CG	N
2.906	73.81	73207	4.00	101.6	2.120	53.8	508	89	1.1	29	570	2536	2.46	62.4	0.393	10.0	6.25	OT	CG	N
2.906	73.81	73178	5.00	127.0	2.344	59.5	90	16	2.6	65	230	1023	2.11	53.6	0.281	7.1	7.51	OT	CG	N
2.906	73.81	73184	5.00	127.0	2.282	58.0	142	25	2.1	54	304	1353	2.34	59.4	0.312	7.9	7.50	OT	CG	N
2.906	73.81	73190	5.00	127.0	2.220	56.4	211	37	1.9	47	392	1746	2.61	66.2	0.343	8.7	7.60	OT	CG	N
2.906	73.81	73196	5.00	127.0	2.182	55.4	273	48	1.7	43	459	2044	2.71	68.9	0.362	9.2	7.49	OT	CG	N
2.906	73.81	73202	5.00	127.0	2.156	54.8	312	55	1.6	41	509	2266	2.86	72.6	0.375	9.5	7.62	OT	CG	N
2.906	73.81	73208	5.00	127.0	2.120	53.8	384	67	1.5	38	570	2536	3.00	76.1	0.393	10.0	7.63	OT	CG	N
2.906	73.81	73213	5.00	127.0	2.094	53.2	435	76	1.4	37	627	2788	3.14	79.9	0.406	10.3	7.75	OT	CG	N
2.906	73.81	73219	5.00	127.0	2.032	51.6	633	111	1.2	30	757	3368	3.28	83.3	0.437	11.1	7.50	OT	CG	N
2.906	73.81	73225	5.00	127.0	1.970	50.0	865	151	1.1	27	923	4105	3.51	89.2	0.468	11.9	7.50	OT	CG	N
2.906	73.81	73231	5.00	127.0	1.906	48.4	1228	215	.87	22	1074	4779	3.63	92.1	0.500	12.7	7.25	OT	CG	N
2.906	73.81	73237	5.00	127.0	1.844	46.8	1625	285	.79	20	1276	5674	3.85	97.8	0.531	13.5	7.25	OT	CG	N
2.906	73.81	73179	6.00	152.4	2.344	59.5	73	13	3.2	80	230	1023	2.47	62.7	0.281	7.1	8.79	OT	CG	N
2.906	73.81	73185	6.00	152.4	2.282	58.0	116	20	2.6	67	304	1353	2.72	69.2	0.312	7.9	8.73	OT	CG	N
2.906	73.81	73191	6.00	152.4	2.220	56.4	172	30	2.3	58	392	1746	3.04	77.3	0.343					




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
2.906	73.81	73230	12.0	304.8	1.970	50.0	317	56	2.9	74	923	4105	7.96	202.2	0.468	11.9	17.0	OT	CG	N
2.906	73.81	73236	12.0	304.8	1.906	48.4	445	78	2.4	61	1074	4779	8.25	209.5	0.500	12.7	16.5	OT	CG	N
2.906	73.81	73242	12.0	304.8	1.844	46.8	583	102	2.2	56	1276	5674	8.83	224.3	0.531	13.5	16.6	OT	CG	N
2.938	74.63	10799	3.25	82.6	2.728	69.3	2.7	.48	2.8	71	7.6	34	.47	12.0	0.105	2.7	4.50	SST	CG	N
2.938	74.63	12628	3.38	85.7	2.524	64.1	52	9.1	1.7	43	88	391	.93	23.7	0.207	5.3	4.50	SPR	CG	Z
2.938	74.63	11779	5.81	147.6	2.564	65.1	11	1.8	3.9	100	42	185	1.87	47.5	0.187	4.7	10.0	SPR	CG	Z
2.938	74.63	4055	8.00	203.2	1.564	39.7	3509	615	.59	15	2088	9287	6.87	174.5	0.687	17.4	10.0	HD	CG	N
2.938	74.63	S-3153	10.5	266.7	2.564	65.1	9.2	1.6	6.1	155	56	249	1.87	47.5	0.187	4.7	10.0	SST	CG	N
2.984	75.79	12443	7.00	177.8	2.782	70.7	1.0	.18	6.1	156	6.2	28	.86	21.8	0.101	2.6	7.50	SST	C	N
3.000	76.20	4138	1.75	44.5	2.586	65.7	81	14	1.0	26	83	368	.72	18.4	0.207	5.3	3.50	SPR	CG	Z
3.000	76.20	11357	2.00	50.8	2.376	60.4	561	98	.47	12	262	1167	1.01	25.8	0.312	7.9	3.25	SPR	CG	Z
3.000	76.20	S-3221	2.72	69.0	2.618	66.5	31	5.4	1.9	47	57	253	.86	21.8	0.191	4.9	4.50	SST	CG	N
3.000	76.20	S-3030	9.00	228.6	2.616	66.4	13	2.2	4.6	118	59	264	1.54	39.0	0.192	4.9	8.00	SST	CG	N
3.000	76.20	4241	11.0	279.4	2.616	66.4	9.8	1.7	7.0	179	69	307	2.11	53.6	0.192	4.9	11.0	SPR	CG	Z
3.031	76.99	S-3218	2.25	57.2	2.595	65.9	43	7.6	1.2	29	50	222	1.09	27.7	0.218	5.5	5.00	SST	CG	N
3.031	76.99	4249	4.63	117.5	2.345	59.6	341	60	.98	25	335	1492	1.72	43.6	0.343	8.7	5.00	SPR	CG	Z
3.125	79.38	11570	2.09	53.2	2.929	74.4	2.4	.42	1.6	41	3.8	17	.49	12.4	0.098	2.5	4.00	SPR	CG	N
3.125	79.38	10819	4.69	119.0	2.313	58.8	486	85	1.1	27	521	2319	2.44	61.9	0.406	10.3	6.00	SPR	CG	N
3.140	79.76	11606	1.50	38.1	2.764	70.2	23	4.1	.37	9.4	8.7	39	1.13	28.7	0.188	4.8	5.00	SPR	CG	Z
3.156	80.16	S-992	1.88	47.6	2.832	71.9	32	5.6	1.2	29	37	164	.49	12.3	0.162	4.1	3.00	SST	CG	N
3.156	80.16	S-249	3.19	81.0	2.860	72.6	11	1.9	2.6	66	29	128	.59	15.0	0.148	3.8	4.00	SST	CG	N
3.156	80.16	73243	5.00	127.0	2.470	62.7	179	31	2.0	52	363	1616	2.40	61.0	0.343	8.7	7.00	OT	CG	N
3.156	80.16	73249	5.00	127.0	2.432	61.8	226	40	1.9	48	426	1893	2.53	64.4	0.362	9.2	7.00	OT	CG	N
3.156	80.16	73255	5.00	127.0	2.406	61.1	264	46	1.8	45	472	2099	2.63	66.7	0.375	9.5	7.00	OT	CG	N
3.156	80.16	73261	5.00	127.0	2.370	60.2	325	57	1.6	41	529	2351	2.75	69.9	0.393	10.0	7.00	OT	CG	N
3.156	80.16	73267	5.00	127.0	2.344	59.5	376	66	1.5	39	581	2585	2.84	72.2	0.406	10.3	7.00	OT	CG	N
3.156	80.16	73273	5.00	127.0	2.282	58.0	522	91	1.3	34	703	3126	3.06	77.7	0.437	11.1	7.00	OT	CG	N
3.156	80.16	73279	5.00	127.0	2.220	56.4	710	124	1.2	31	858	3814	3.28	83.2	0.468	11.9	7.00	OT	CG	N
3.156	80.16	73285	5.00	127.0	2.156	54.8	959	168	1.0	26	999	4446	3.50	88.9	0.500	12.7	7.00	OT	CG	N
3.156	80.16	73291	5.00	127.0	2.094	53.2	1264	221	.94	24	1188	5286	3.72	94.4	0.531	13.5	7.00	OT	CG	N
3.156	80.16	4023-A	5.50	139.7	1.968	49.9	2003	351	.87	22	1750	7784	4.34	110.2	0.594	15.1	7.31	SPR	CG	N
3.156	80.16	73244	6.00	152.4	2.470	62.7	146	26	2.5	63	363	1616	2.79	70.8	0.343	8.7	8.12	OT	CG	N
3.156	80.16	73250	6.00	152.4	2.432	61.8	185	32	2.3	58	426	1893	2.94	74.7	0.362	9.2	8.12	OT	CG	N
3.156	80.16	73256	6.00	152.4	2.406	61.1	212	37	2.2	57	472	2099	3.09	78.6	0.375	9.5	8.25	OT	CG	N
3.156	80.16	73262	6.00	152.4	2.370	60.2	260	46	2.0	52	529	2351	3.24	82.4	0.393	10.0	8.25	OT	CG	N
3.156	80.16	73268	6.00	152.4	2.344	59.5	350	61	1.7	42	581	2585	2.99	76.0	0.406	10.				



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
3.250	82.55	4096	12.0	304.8	2.250	57.2	411	72	2.1	53	866	3850	6.25	158.8	0.500	12.7	12.5	SPR	CG	N
3.266	82.96	S-1635	6.75	171.5	2.330	59.2	632	111	.89	23	562	2501	2.96	75.2	0.468	11.9	6.33	SST	CG	N
3.328	84.53	10985	3.13	79.4	2.828	71.8	59	10	1.9	47	111	492	1.22	31.0	0.250	6.4	5.00	SST	CG	N
3.375	85.73	4347	5.25	133.4	2.991	76.0	22	3.9	2.8	71	61	273	.91	23.2	0.192	4.9	4.75	SPR	CG	Z
3.375	85.73	S-3020	5.50	139.7	3.125	79.4	3.0	.52	4.8	121	14	63	.75	19.1	0.125	3.2	5.00	SST	C	N
3.375	85.73	4090	14.0	355.6	2.501	63.5	207	36	2.8	72	588	2614	5.24	133.2	0.437	11.1	12.0	SPR	CG	N
3.406	86.51	73297	6.00	152.4	2.720	69.1	121	21	2.8	71	338	1504	2.65	67.3	0.343	8.7	7.72	OT	CG	N
3.406	86.51	73303	6.00	152.4	2.682	68.1	152	27	2.6	66	396	1763	2.81	71.3	0.362	9.2	7.76	OT	CG	N
3.406	86.51	73309	6.00	152.4	2.656	67.5	177	31	2.5	63	440	1955	2.91	74.0	0.375	9.5	7.77	OT	CG	N
3.406	86.51	73315	6.00	152.4	2.620	66.5	209	37	2.4	60	492	2191	3.14	79.8	0.393	10.0	8.00	OT	CG	N
3.406	86.51	73321	6.00	152.4	2.594	65.9	241	42	2.2	57	542	2410	3.25	82.5	0.406	10.3	8.00	OT	CG	N
3.406	86.51	73327	6.00	152.4	2.532	64.3	341	60	1.9	49	656	2916	3.44	87.4	0.437	11.1	7.87	OT	CG	N
3.406	86.51	73333	6.00	152.4	2.470	62.7	473	83	1.7	43	800	3560	3.63	92.1	0.468	11.9	7.75	OT	CG	N
3.406	86.51	73339	6.00	152.4	2.406	61.1	637	112	1.5	37	934	4154	3.87	98.4	0.500	12.7	7.75	OT	CG	N
3.406	86.51	73345	6.00	152.4	2.344	59.5	855	150	1.3	33	1111	4943	4.05	102.8	0.531	13.5	7.63	OT	CG	N
3.406	86.51	73351	6.00	152.4	2.282	58.0	1103	193	1.2	30	1292	5746	4.30	109.2	0.562	14.3	7.65	OT	CG	N
3.406	86.51	73357	6.00	152.4	2.220	56.4	1465	257	1.0	26	1477	6571	4.42	112.2	0.593	15.1	7.45	OT	CG	N
3.406	86.51	73298	8.00	203.2	2.720	69.1	89	16	3.8	97	338	1504	3.35	85.2	0.343	8.7	9.78	OT	CG	N
3.406	86.51	73304	8.00	203.2	2.682	68.1	109	19	3.6	92	396	1763	3.63	92.2	0.362	9.2	10.0	OT	CG	N
3.406	86.51	73310	8.00	203.2	2.656	67.5	127	22	3.5	88	440	1955	3.76	95.6	0.375	9.5	10.0	OT	CG	N
3.406	86.51	73316	8.00	203.2	2.620	66.5	152	27	3.2	82	492	2191	4.03	102.3	0.393	10.0	10.2	OT	CG	N
3.406	86.51	73322	8.00	203.2	2.594	65.9	175	31	3.1	79	542	2410	4.17	105.9	0.406	10.3	10.3	OT	CG	N
3.406	86.51	73328	8.00	203.2	2.532	64.3	243	43	2.7	69	656	2916	4.48	113.7	0.437	11.1	10.2	OT	CG	N
3.406	86.51	73334	8.00	203.2	2.470	62.7	340	60	2.4	60	800	3560	4.68	118.8	0.468	11.9	10.0	OT	CG	N
3.406	86.51	73340	8.00	203.2	2.406	61.1	457	80	2.0	52	934	4154	5.01	127.1	0.500	12.7	10.0	OT	CG	N
3.406	86.51	73346	8.00	203.2	2.344	59.5	608	106	1.8	46	1111	4943	5.26	133.7	0.531	13.5	9.91	OT	CG	N
3.406	86.51	73352	8.00	203.2	2.282	58.0	779	136	1.7	42	1292	5746	5.62	142.8	0.562	14.3	10.0	OT	CG	N
3.406	86.51	73358	8.00	203.2	2.220	56.4	1037	182	1.4	36	1477	6571	5.75	146.1	0.593	15.1	9.70	OT	CG	N
3.406	86.51	73299	10.0	254.0	2.720	69.1	71	12	4.8	121	338	1504	4.03	102.4	0.343	8.7	11.8	OT	CG	N
3.406	86.51	73305	10.0	254.0	2.682	68.1	85	15	4.7	118	396	1763	4.45	113.1	0.362	9.2	12.3	OT	CG	N
3.406	86.51	73311	10.0	254.0	2.656	67.5	100	18	4.4	112	440	1955	4.58	116.3	0.375	9.5	12.2	OT	CG	N
3.406	86.51	73317	10.0	254.0	2.620	66.5	119	21	4.1	105	492	2191	4.93	125.1	0.393	10.0	12.5	OT	CG	N
3.406	86.51	73323	10.0	254.0	2.594	65.9	138	24	3.9	100	542	2410	5.07	128.7	0.406	10.3	12.5	OT	CG	N
3.406	86.51	73329	10.0	254.0	2.532	64.3	191	33	3.4	87	656	2916	5.46	138.6	0.437	11.1	12.5	OT	CG	N
3.406	86.51	73335	10.0	254.0	2.470	62.7	265	46	3.0	77	800	3560	5.74	145.7	0.468	11.9	12.3	OT	CG	N
3.406	86.51	73341	10.0	254.0	2.406	61.1	353	62	2.6	67	934	4154	6.19	157.1	0.500	12.7	12.4	OT	CG	N
3.406	86.51	73347	10.0	254.0	2.344	59.5	469	82	2.4	60	1111	4943	6.51	165.3	0.531	13.5	12.3	OT	CG	N
3.406	86.51	73353	10.0	254.0	2.282	58.0	608	106	2.1	54	1292	5746	6.89	174.9	0.562	14.3	12.3	OT	CG	N
3.406	86.51	73359	10.0	254.0	2.220	56.4	798	140	1.9	47	1477	6571	7.12	180.9	0.593	15.1	12.0	OT	CG	N
3.406	86.51	73300	12.0	304.8	2.720	69.1	59	10	5.7	146	338	1504	4.71	119.7	0.343	8.7	13.7	OT	CG	N
3.406	86.51	73306	12.0	304.8	2.682	68.1	71	12	5.6	142	396	1763	5.19	131.7	0.362	9.2	14.3	OT	CG	N
3.406	86.51	73312	12.0	304.8	2.656	67.5	82	14	5.4	136	440	1955	5.42	137.6	0.375	9.5	14.5	OT	CG	N
3.406	86.51	73318	12.0	304.8	2.620	66.5	98	17	5.0	128	492	2191	5.81	147.7	0.393	10.0	14.8	OT	CG	N
3.406	86.51	73324	12.0	304.8	2.594	65.9	112	20	4.8	123	542	2410	6.06	153.8	0.406	10.3	14.9	OT	CG	N
3.406	86.51	73330	12.0	304.8	2.532	64.3	157	27	4.2	106	656	2916	6.45	163.8	0.437	11.1	14.8	OT	CG	N
3.406	86.51	73336	12.0	304.8	2.470	62.7	218	38	3.7	93	800	3560	6.77	172.0	0.468	11.9	14.5	OT	CG	N
3.406	86.51	73342	12.0	304.8	2.406	61.1	290	51	3.2	82	934	4154	7.31	185.7	0.500	12.7	14.6	OT	CG	N
3.406	86.51	73348	12.0	304.8	2.344	59.5	385	67	2.9	73	1111	4943	7.69	195.4	0.531	13.5	14.5	OT	CG	N
3.406	86.51	73354	12.0	304.8	2.282	58.0	494	87	2.6	66	1292	5746	8.22	208.7	0.562	14.3	14.6	OT	CG	N
3.406	86.51	73360	12.0	304.8	2.220	56.4	652	114	2.3	58	1477	6571	8.45	214.6	0.593	15.1	14.2	OT	CG	N
3.406	86.51	73301	14.0	355.6	2.720	69.1	49	8.6	6.9	175	338	1504	5.53	140.5	0.343	8.7	16.1	OT	CG	N
3.406	86.51	73307	14.0	355.6	2.682	68.1	59	10	6.7	171	396	1763	6.09	154.8	0.362	9.2	16.8	OT	CG	N
3.406	86.51	73313	14.0	355.6	2.656	67.5	69	12	6.4	162	440	1955	6.30	160.0	0.375	9.5	16.8	OT	CG	N
3.406	86.51	73319	14.0	355.6	2.620	66.5	84	15	5.9	149	492	2191	6.65	168.9						



1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F I N D S	F N S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
3.656	92.86	73369	6.00	152.4	2.906	73.8	161	28	2.6	65	411	1829	2.62	66.7	0.375	9.5	7.00	OT	CG	N
3.656	92.86	73375	6.00	152.4	2.870	72.9	197	35	2.3	59	461	2050	2.75	69.9	0.393	10.0	7.00	OT	CG	N
3.656	92.86	73381	6.00	152.4	2.844	72.2	228	40	2.2	57	507	2256	2.84	72.2	0.406	10.3	7.00	OT	CG	N
3.656	92.86	73387	6.00	152.4	2.782	70.7	299	52	2.1	52	614	2731	3.17	80.5	0.437	11.1	7.25	OT	CG	N
3.656	92.86	73393	6.00	152.4	2.720	69.1	405	71	1.9	47	750	3337	3.39	86.2	0.468	11.9	7.25	OT	CG	N
3.656	92.86	73399	6.00	152.4	2.656	67.5	544	95	1.6	41	876	3896	3.63	92.1	0.500	12.7	7.25	OT	CG	N
3.656	92.86	73405	6.00	152.4	2.594	65.9	713	125	1.5	37	1043	4640	3.85	97.8	0.531	13.5	7.25	OT	CG	N
3.656	92.86	73411	6.00	152.4	2.532	64.3	922	161	1.3	33	1214	5398	4.07	103.5	0.562	14.3	7.25	OT	CG	N
3.656	92.86	73417	6.00	152.4	2.470	62.7	1207	211	1.2	29	1389	6178	4.23	107.3	0.593	15.1	7.13	OT	CG	N
3.656	92.86	73364	8.00	203.2	2.932	74.5	99	17	3.8	95	371	1649	3.26	82.8	0.362	9.2	9.01	OT	CG	N
3.656	92.86	73370	8.00	203.2	2.906	73.8	117	20	3.5	90	411	1829	3.34	84.8	0.375	9.5	8.90	OT	CG	N
3.656	92.86	73376	8.00	203.2	2.870	72.9	143	25	3.2	82	461	2050	3.50	88.9	0.393	10.0	8.90	OT	CG	N
3.656	92.86	73382	8.00	203.2	2.844	72.2	165	29	3.1	78	507	2256	3.61	91.8	0.406	10.3	8.90	OT	CG	N
3.656	92.86	73388	8.00	203.2	2.782	70.7	217	38	2.8	72	614	2731	4.04	102.7	0.437	11.1	9.25	OT	CG	N
3.656	92.86	73394	8.00	203.2	2.720	69.1	292	51	2.6	65	750	3337	4.35	110.5	0.468	11.9	9.30	OT	CG	N
3.656	92.86	73400	8.00	203.2	2.656	67.5	389	68	2.3	57	876	3896	4.68	118.8	0.500	12.7	9.35	OT	CG	N
3.656	92.86	73406	8.00	203.2	2.594	65.9	506	89	2.1	52	1043	4640	4.99	126.8	0.531	13.5	9.40	OT	CG	N
3.656	92.86	73412	8.00	203.2	2.532	64.3	657	115	1.8	47	1214	5398	5.27	133.8	0.562	14.3	9.38	OT	CG	N
3.656	92.86	73418	8.00	203.2	2.470	62.7	853	149	1.6	41	1389	6178	5.49	139.3	0.593	15.1	9.25	OT	CG	N
3.656	92.86	73365	10.0	254.0	2.932	74.5	78	14	4.7	120	371	1649	3.91	99.4	0.362	9.2	10.8	OT	CG	N
3.656	92.86	73371	10.0	254.0	2.906	73.8	93	16	4.4	113	411	1829	4.01	101.9	0.375	9.5	10.7	OT	CG	N
3.656	92.86	73377	10.0	254.0	2.870	72.9	112	20	4.1	104	461	2050	4.25	107.9	0.393	10.0	10.8	OT	CG	N
3.656	92.86	73383	10.0	254.0	2.844	72.2	129	23	3.9	100	507	2256	4.38	111.4	0.406	10.3	10.8	OT	CG	N
3.656	92.86	73389	10.0	254.0	2.782	70.7	169	30	3.6	92	614	2731	4.94	125.4	0.437	11.1	11.3	OT	CG	N
3.656	92.86	73395	10.0	254.0	2.720	69.1	226	40	3.3	84	750	3337	5.34	135.5	0.468	11.9	11.4	OT	CG	N
3.656	92.86	73401	10.0	254.0	2.656	67.5	304	53	2.9	73	876	3896	5.70	144.8	0.500	12.7	11.4	OT	CG	N
3.656	92.86	73407	10.0	254.0	2.594	65.9	394	69	2.6	67	1043	4640	6.11	155.1	0.531	13.5	11.5	OT	CG	N
3.656	92.86	73413	10.0	254.0	2.532	64.3	507	89	2.4	61	1214	5398	6.49	164.9	0.562	14.3	11.6	OT	CG	N
3.656	92.86	73419	10.0	254.0	2.470	62.7	660	116	2.1	53	1389	6178	6.75	171.3	0.593	15.1	11.4	OT	CG	N
3.656	92.86	73366	12.0	304.8	2.932	74.5	64	11	5.8	147	371	1649	4.62	117.3	0.362	9.2	12.8	OT	CG	N
3.656	92.86	73372	12.0	304.8	2.906	73.8	76	13	5.4	138	411	1829	4.74	120.3	0.375	9.5	12.6	OT	CG	N
3.656	92.86	73378	12.0	304.8	2.870	72.9	92	16	5.0	128	461	2050	5.01	127.3	0.393	10.0	12.8	OT	CG	N
3.656	92.86	73384	12.0	304.8	2.844	72.2	106	19	4.8	122	507	2256	5.18	131.5	0.406	10.3	12.8	OT	CG	N
3.656	92.86	73390	12.0	304.8	2.782	70.7	139	24	4.4	113	614	2731	5.83	148.2	0.437	11.1	13.3	OT	CG	N
3.656	92.86	73396	12.0	304.8	2.720	69.1	185	32	4.1	103	750	3337	6.32	160.5	0.468	11.9	13.5	OT	CG	N
3.656	92.86	73402	12.0	304.8	2.656	67.5	249	44	3.5	90	876	3896	6.75	171.5	0.500	12.7	13.5	OT	CG	N
3.656	92.86	73408	12.0	304.8	2.594	65.9	323	57	3.2	82	1043	4640	7.22	183.4	0.531	13.5	13.6	OT	CG	N
3.656	92.86	73414	12.0	304.8	2.532	64.3	412	72	2.9	75	1214	5398	7.73	196.3	0.562	14.3	13.8	OT	CG	N
3.656	92.86	73420	12.0	304.8	2.470	62.7	538	94	2.6	66	1389	6178	8.01	203.3	0.593	15.1	13.5	OT	CG	N
3.656	92.86	73367	14.0	355.6	2.932	74.5	54	9.5	6.8	174	371	1649	5.34	135.6	0.362	9.2	14.7	OT	CG	N
3.656	92.86	73373	14.0	355.6	2.906	73.8	64	11	6.5	164	411	1829	5.49	139.4	0.375	9.5	14.6	OT	CG	N
3.656	92.86	73379	14.0	355.6	2.870	72.9	78	14	5.9	151	461	2050	5.78	146.8	0.393	10.0	14.7	OT	CG	N
3.656	92.86	73385	14.0	355.6	2.844	72.2	90	16	5.7	144	507	2256	5.97	151.6	0.406	10.3	14.7	OT	CG	N
3.656	92.86	73391	14.0	355.6	2.782	70.7	118	21	5.2	132	614	2731	6.71	170.4	0.437	11.1	15.4	OT	CG	N
3.656	92.86	73397	14.0	355.6	2.720	69.1	158	28	4.8	121	750	3337	7.26	184.3	0.468	11.9	15.5	OT	CG	N
3.656	92.86	73403	14.0	355.6	2.656	67.5	210	37	4.2	106	876	3896	7.80	198.2	0.500	12.7	15.6	OT	CG	N
3.656	92.86	73409	14.0	355.6	2.594	65.9	272	48	3.8	97	1043	4640	8.36	212.5	0.531	13.5	15.8	OT	CG	N
3.656	92.86	73415	14.0	355.6	2.532	64.3	349	61	3.5	88	1214	5398	8.92	226.6	0.562	14.3	15.9	OT	CG	N
3.656	92.86	73421	14.0	355.6	2.470	62.7	454	80	3.1	78	1389	6178	9.27	235.3	0.593	15.1	15.6	OT	CG	N
3.656	92.86	73368	16.0	406.4	2.932	74.5	47	8.2	7.9	201	371	1649	6.07	154.1	0.362	9.2	16.8	OT	CG	N
3.656	92.86	73374	16.0	406.4	2.906	73.8	56	9.7	7.4	188	411	1829	6.19	157.2	0.375	9.5	16.5	OT	CG	N
3.656	92.86	73380	16.0	406.4	2.870	72.9	68	12	6.8	173	461	2050	6.53	165.9	0.393	10.0	16.6	OT	CG	N
3.656	92.86	73386	16.0	406.4	2.844	72.2	78	14	6.5	166	507	2256	6.75	171.4	0.406	10.3	16.6	OT	CG	N
3.656	92.86	73392	16.0	406.4	2.782	70.7	102	18	6.0	153	614	2731	7.61	193.2	0.437	11.1	17.4	OT	CG	N



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
3.906	99.21	73448	8.00	203.2	2.970	75.4	242	42	2.9	74	706	3139	4.22	107.1	0.468	11.9	9.01	OT	CG	N
3.906	99.21	73454	8.00	203.2	2.906	73.8	325	57	2.5	64	824	3667	4.50	114.2	0.500	12.7	9.00	OT	CG	N
3.906	99.21	73460	8.00	203.2	2.844	72.2	425	74	2.3	59	982	4370	4.78	121.3	0.531	13.5	9.00	OT	CG	N
3.906	99.21	73466	8.00	203.2	2.782	70.7	548	96	2.1	53	1144	5087	5.06	128.4	0.562	14.3	9.00	OT	CG	N
3.906	99.21	73472	8.00	203.2	2.720	69.1	699	122	1.9	48	1310	5827	5.33	135.5	0.593	15.1	8.99	OT	CG	N
3.906	99.21	73478	8.00	203.2	2.656	67.5	920	161	1.7	42	1525	6782	5.47	138.9	0.625	15.9	8.75	OT	CG	N
3.906	99.21	73425	10.0	254.0	3.156	80.2	78	14	5.0	126	386	1718	3.85	97.9	0.375	9.5	10.3	OT	CG	N
3.906	99.21	73431	10.0	254.0	3.120	79.2	96	17	4.5	115	433	1926	4.02	102.2	0.393	10.0	10.2	OT	CG	N
3.906	99.21	73437	10.0	254.0	3.094	78.6	107	19	4.5	113	477	2120	4.27	108.4	0.406	10.3	10.5	OT	CG	N
3.906	99.21	73443	10.0	254.0	3.032	77.0	143	25	4.0	103	577	2568	4.71	119.7	0.437	11.1	10.8	OT	CG	N
3.906	99.21	73449	10.0	254.0	2.970	75.4	189	33	3.7	95	706	3139	5.14	130.5	0.468	11.9	11.0	OT	CG	N
3.906	99.21	73455	10.0	254.0	2.906	73.8	253	44	3.3	83	824	3667	5.49	139.5	0.500	12.7	11.0	OT	CG	N
3.906	99.21	73461	10.0	254.0	2.844	72.2	330	58	3.0	76	982	4370	5.85	148.5	0.531	13.5	11.0	OT	CG	N
3.906	99.21	73467	10.0	254.0	2.782	70.7	420	74	2.7	69	1144	5087	6.26	158.9	0.562	14.3	11.1	OT	CG	N
3.906	99.21	73473	10.0	254.0	2.720	69.1	536	94	2.4	62	1310	5827	6.59	167.5	0.593	15.1	11.1	OT	CG	N
3.906	99.21	73479	10.0	254.0	2.656	67.5	710	124	2.1	55	1525	6782	6.72	170.6	0.625	15.9	10.7	OT	CG	N
3.906	99.21	73426	12.0	304.8	3.156	80.2	65	11	5.9	151	386	1718	4.48	113.7	0.375	9.5	11.9	OT	CG	N
3.906	99.21	73432	12.0	304.8	3.120	79.2	79	14	5.5	139	433	1926	4.72	119.9	0.393	10.0	12.0	OT	CG	N
3.906	99.21	73438	12.0	304.8	3.094	78.6	88	15	5.4	138	477	2120	5.01	127.4	0.406	10.3	12.4	OT	CG	N
3.906	99.21	73444	12.0	304.8	3.032	77.0	120	21	4.8	122	577	2568	5.45	138.4	0.437	11.1	12.5	OT	CG	N
3.906	99.21	73450	12.0	304.8	2.970	75.4	154	27	4.6	116	706	3139	6.09	154.8	0.468	11.9	13.0	OT	CG	N
3.906	99.21	73456	12.0	304.8	2.906	73.8	207	36	4.0	101	824	3667	6.49	164.9	0.500	12.7	13.0	OT	CG	N
3.906	99.21	73462	12.0	304.8	2.844	72.2	270	47	3.6	92	982	4370	6.91	175.5	0.531	13.5	13.0	OT	CG	N
3.906	99.21	73468	12.0	304.8	2.782	70.7	345	60	3.3	84	1144	5087	7.37	187.2	0.562	14.3	13.1	OT	CG	N
3.906	99.21	73474	12.0	304.8	2.720	69.1	439	77	3.0	76	1310	5827	7.79	197.8	0.593	15.1	13.1	OT	CG	N
3.906	99.21	73480	12.0	304.8	2.656	67.5	578	101	2.6	67	1525	6782	7.97	202.3	0.625	15.9	12.7	OT	CG	N
3.906	99.21	73427	14.0	355.6	3.156	80.2	54	9.5	7.2	182	386	1718	5.23	132.9	0.375	9.5	14.0	OT	CG	N
3.906	99.21	73433	14.0	355.6	3.120	79.2	66	12	6.6	167	433	1926	5.50	139.6	0.393	10.0	14.0	OT	CG	N
3.906	99.21	73439	14.0	355.6	3.094	78.6	74	13	6.4	164	477	2120	5.81	147.6	0.406	10.3	14.3	OT	CG	N
3.906	99.21	73445	14.0	355.6	3.032	77.0	100	18	5.8	147	577	2568	6.36	161.6	0.437	11.1	14.6	OT	CG	N
3.906	99.21	73451	14.0	355.6	2.970	75.4	131	23	5.4	137	706	3139	7.00	177.8	0.468	11.9	15.0	OT	CG	N
3.906	99.21	73457	14.0	355.6	2.906	73.8	175	31	4.7	120	824	3667	7.50	190.4	0.500	12.7	15.0	OT	CG	N
3.906	99.21	73463	14.0	355.6	2.844	72.2	229	40	4.3	109	982	4370	7.96	202.1	0.531	13.5	15.0	OT	CG	N
3.906	99.21	73469	14.0	355.6	2.782	70.7	289	51	4.0	101	1144	5087	8.58	218.0	0.562	14.3	15.3	OT	CG	N
3.906	99.21	73475	14.0	355.6	2.720	69.1	369	65	3.6	90	1310	5827	9.04	229.7	0.593	15.1	15.2	OT	CG	N
3.906	99.21	73481	14.0	355.6	2.656	67.5	487	85	3.1	80	1525	6782	9.22	234.2	0.625	15.9	14.8	OT	CG	N
3.906	99.21	73428	16.0	406.4	3.156	80.2	47	8.2	8.2	209	386	1718	5.90	149.9	0.375	9.5	15.7	OT	CG	N
3.906	99.21	73434	16.0	406.4	3.120	79.2	57	10	7.6	193	433	1926	6.24	158.5	0.393	10.0	15.9	OT	CG	N
3.906	99.21	73440	16.0	406.4	3.094	78.6	64	11	7.4	189	477	2120	6.59	167.4	0.406	10.3	16.2	OT	CG	N
3.906	99.21	73446	16.0	406.4	3.032	77.0	87	15	6.6	169	577	2568	7.18	182.4	0.437	11.1	16.4	OT	CG	N
3.906	99.21	73452	16.0	406.4	2.970	75.4	113	20	6.2	159	706	3139	7.96	202.3	0.468	11.9	17.0	OT	CG	N
3.906	99.21	73458	16.0	406.4	2.906	73.8	152	27	5.4	138	824	3667	8.48	215.4	0.500	12.7	17.0	OT	CG	N
3.906	99.21	73464	16.0	406.4	2.844	72.2	198	35	5.0	126	982	4370	9.03	229.5	0.531	13.5	17.0	OT	CG	N
3.906	99.21	73470	16.0	406.4	2.782	70.7	251	44	4.6	116	1144	5087	9.71	246.6	0.562	14.3	17.3	OT	CG	N
3.906	99.21	73476	16.0	406.4	2.720	69.1	321	56	4.1	104	1310	5827	10.2	259.5	0.593	15.1	17.2	OT	CG	N
3.906	99.21	73482	16.0	406.4	2.656	67.5	421	74	3.6	92	1525	6782	10.5	265.9	0.625	15.9	16.8	OT	CG	N
3.968	100.79	S-1596	3.50	88.9	3.728	94.7	.41	.07	1.9	49	.80	3.5	1.56	39.6	0.120	3.0	13.0	SST	CG	N
4.000	101.60	4052	4.25	108.0	2.000	50.8	26620	4662	.14	3.5	3645	16214	4.00	101.6	1.000	25.4	4.00	HD	CG	N
4.000	101.60	4030	6.00	152.4	3.338	84.8	116	20	2.0	52	238	1057	1.66	42.0	0.331	8.4	5.00	SPR	CG	Z
4.000	101.60	4082	6.25	158.8	2.812	71.4	2265	397	.51	13	1145	5095	2.38	60.4	0.594	15.1	4.00	HD	CG	N
4.000	101.60	4020	6.25	158.8	2.750	69.9	1201	210	1.1	28	1327	5903	4.22	107.2	0.625	15.9	6.75	SPR	CG	N
4.000	101.60	4048	10.0	254.0	2.500	63.5	2208	387	.88	22	1939	8625	6.00	152.4	0.750	19.1	8.00	SPR	CG	N
4.125	104.78	4406	4.00	101.6	3.713	94.3	17	3.0	3.1	78	52	231	.92	23.4	0.206	5.2	4.50	SPR	CG	Z
4.125	104.78	11302	4.00	101.6	3.375	85.7	127	22												




1-800-237-5225
1-213-749-1466
 Fax (213) 749-3802
 www.centuryspring.com

COMPRESSION SPRINGS

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	F N D S	F N H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
4.156	105.56	73527	10.0	254.0	3.032	77.0	377	66	2.9	73	1081	4809	5.73	145.6	0.562	14.3	10.2	OT	CG	N
4.156	105.56	73533	10.0	254.0	2.970	75.4	476	83	2.6	66	1239	5511	6.08	154.4	0.593	15.1	10.3	OT	CG	N
4.156	105.56	73486	12.0	304.8	3.406	86.5	58	10	6.3	161	364	1620	4.17	106.0	0.375	9.5	11.1	OT	CG	N
4.156	105.56	73492	12.0	304.8	3.370	85.6	71	12	5.8	147	408	1816	4.37	111.1	0.393	10.0	11.1	OT	CG	N
4.156	105.56	73498	12.0	304.8	3.344	84.9	76	13	5.9	150	449	1999	4.77	121.1	0.406	10.3	11.7	OT	CG	N
4.156	105.56	73504	12.0	304.8	3.282	83.4	105	18	5.2	132	545	2423	5.14	130.5	0.437	11.1	11.8	OT	CG	N
4.156	105.56	73510	12.0	304.8	3.220	81.8	141	25	4.7	120	666	2963	5.50	139.7	0.468	11.9	11.8	OT	CG	N
4.156	105.56	73516	12.0	304.8	3.156	80.2	175	31	4.4	113	778	3463	6.25	158.8	0.500	12.7	12.5	OT	CG	N
4.156	105.56	73522	12.0	304.8	3.094	78.6	240	42	3.9	98	928	4129	6.37	161.8	0.531	13.5	12.0	OT	CG	N
4.156	105.56	73528	12.0	304.8	3.032	77.0	309	54	3.5	89	1081	4809	6.74	171.3	0.562	14.3	12.0	OT	CG	N
4.156	105.56	73534	12.0	304.8	2.970	75.4	388	68	3.2	81	1239	5511	7.19	182.6	0.593	15.1	12.1	OT	CG	N
4.156	105.56	73487	14.0	355.6	3.406	86.5	49	8.6	7.4	189	364	1620	4.78	121.5	0.375	9.5	12.8	OT	CG	N
4.156	105.56	73493	14.0	355.6	3.370	85.6	60	10	6.8	173	408	1816	5.02	127.4	0.393	10.0	12.8	OT	CG	N
4.156	105.56	73499	14.0	355.6	3.344	84.9	65	11	6.9	175	449	1999	5.43	137.9	0.406	10.3	13.4	OT	CG	N
4.156	105.56	73505	14.0	355.6	3.282	83.4	89	16	6.1	156	545	2423	5.90	149.9	0.437	11.1	13.5	OT	CG	N
4.156	105.56	73511	14.0	355.6	3.220	81.8	120	21	5.6	142	666	2963	6.32	160.5	0.468	11.9	13.5	OT	CG	N
4.156	105.56	73517	14.0	355.6	3.156	80.2	150	26	5.2	132	778	3463	7.12	181.0	0.500	12.7	14.2	OT	CG	N
4.156	105.56	73523	14.0	355.6	3.094	78.6	204	36	4.5	115	928	4129	7.30	185.4	0.531	13.5	13.7	OT	CG	N
4.156	105.56	73529	14.0	355.6	3.032	77.0	260	46	4.2	106	1081	4809	7.80	198.1	0.562	14.3	13.9	OT	CG	N
4.156	105.56	73535	14.0	355.6	2.970	75.4	328	57	3.8	96	1239	5511	8.30	210.9	0.593	15.1	14.0	OT	CG	N
4.156	105.56	73488	16.0	406.4	3.406	86.5	43	7.5	8.5	216	364	1620	5.35	135.8	0.375	9.5	14.3	OT	CG	N
4.156	105.56	73494	16.0	406.4	3.370	85.6	52	9.0	7.9	201	408	1816	5.70	144.7	0.393	10.0	14.5	OT	CG	N
4.156	105.56	73500	16.0	406.4	3.344	84.9	56	9.9	8.0	202	449	1999	6.14	156.0	0.406	10.3	15.1	OT	CG	N
4.156	105.56	73506	16.0	406.4	3.282	83.4	77	13	7.1	180	545	2423	6.67	169.3	0.437	11.1	15.3	OT	CG	N
4.156	105.56	73512	16.0	406.4	3.220	81.8	104	18	6.4	163	666	2963	7.14	181.4	0.468	11.9	15.3	OT	CG	N
4.156	105.56	73518	16.0	406.4	3.156	80.2	129	23	6.0	153	778	3463	8.13	206.4	0.500	12.7	16.3	OT	CG	N
4.156	105.56	73524	16.0	406.4	3.094	78.6	176	31	5.3	134	928	4129	8.28	210.4	0.531	13.5	15.6	OT	CG	N
4.156	105.56	73530	16.0	406.4	3.032	77.0	225	39	4.8	122	1081	4809	8.85	224.9	0.562	14.3	15.8	OT	CG	N
4.156	105.56	73536	16.0	406.4	2.970	75.4	283	50	4.4	111	1239	5511	9.42	239.1	0.593	15.1	15.9	OT	CG	N
4.250	107.95	4021	10.8	273.1	2.250	57.2	6979	1222	.50	13	3492	15531	8.00	203.2	1.000	25.4	8.00	SPR	CG	N
4.375	111.13	4022	8.00	203.2	2.499	63.5	6091	1067	.47	12	2863	12733	6.10	154.9	0.938	23.8	6.50	SPR	CG	N
4.406	111.91	73537	6.00	152.4	3.532	89.7	197	34	2.6	66	515	2293	2.73	69.4	0.437	11.1	6.26	OT	CG	N
4.406	111.91	73543	6.00	152.4	3.470	88.1	266	47	2.4	60	631	2805	2.92	74.2	0.468	11.9	6.25	OT	CG	N
4.406	111.91	73549	6.00	152.4	3.406	86.5	355	62	2.1	53	737	3280	3.12	79.3	0.500	12.7	6.25	OT	CG	N
4.406	111.91	73555	6.00	152.4	3.344	84.9	462	81	1.9	48	879	3912	3.32	84.3	0.531	13.5	6.25	OT	CG	N
4.406	111.91	73561	6.00	152.4	3.282	83.4	594	104	1.7	44	1025	4558	3.51	89.2	0.562	14.3	6.25	OT	CG	N
4.406	111.91	73567	6.00	152.4	3.220	81.8	754	132	1.6	40	1175	5226	3.71	94.2	0.593	15.1	6.25	OT	CG	N
4.406	111.91	73573	6.00	152.4	3.156	80.2	955	167	1.4	36	1369	6089	3.91	99.2	0.625	15.9	6.25	OT	CG	N
4.406	111.91	73538	8.00	203.2	3.532	89.7	143	25	3.6	92	515	2293	3.44	87.3	0.437	11.1	7.86	OT	CG	N
4.406	111.91	73544	8.00	203.2	3.470	88.1	188	33	3.4	85	631	2805	3.75	95.2	0.468	11.9	8.01	OT	CG	N
4.406	111.91	73550	8.00	203.2	3.406	86.5	251	44	2.9	75	737	3280	4.00	101.7	0.500	12.7	8.01	OT	CG	N
4.406	111.91	73556	8.00	203.2	3.344	84.9	327	57	2.7	68	879	3912	4.25	108.0	0.531	13.5	8.01	OT	CG	N
4.406	111.91	73562	8.00	203.2	3.282	83.4	421	74	2.4	62	1025	4558	4.49	114.2	0.562	14.3	8.00	OT	CG	N
4.406	111.91	73568	8.00	203.2	3.220	81.8	534	94	2.2	56	1175	5226	4.75	120.6	0.593	15.1	8.01	OT	CG	N
4.406	111.91	73574	8.00	203.2	3.156	80.2	676	118	2.0	51	1369	6089	5.00	127.0	0.625	15.9	8.00	OT	CG	N
4.406	111.91	73539	10.0	254.0	3.532	89.7	112	20	4.6	117	515	2293	4.15	105.3	0.437	11.1	9.49	OT	CG	N
4.406	111.91	73545	10.0	254.0	3.470	88.1	146	26	4.3	110	631	2805	4.56	115.7	0.468	11.9	9.73	OT	CG	N
4.406	111.91	73551	10.0	254.0	3.406	86.5	195	34	3.8	96	737	3280	4.87	123.6	0.500	12.7	9.73	OT	CG	N
4.406	111.91	73557	10.0	254.0	3.344	84.9	253	44	3.5	88	879	3912	5.18	131.7	0.531	13.5	9.76	OT	CG	N
4.406	111.91	73563	10.0	254.0	3.282	83.4	326	57	3.1	80	1025	4558	5.48	139.1	0.562	14.3	9.74	OT	CG	N
4.406	111.91	73569	10.0	254.0	3.220	81.8	414	72	2.8	72	1175	5226	5.78	146.8	0.593	15.1	9.75	OT	CG	N
4.406	111.91	73575	10.0	254.0	3.156	80.2	524	92	2.6	66	1369	6089	6.09	154.7	0.625	15.9	9.74	OT	CG	N
4.406	111.91	73540	12.0	304.8	3.532	89.7	93	16	5.5	141	515	2293	4.81	122.3	0.437	11.1	11.0	OT	CG	N
4.406	111.91	73546	12.0	304.8	3.470	88.1	122	21	5.2	131	631	2805	5							



O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F I N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
4.687	119.05	73585	6.00	152.4	3.875	98.4	137	24	2.9	74	401	1783	2.28	58.0	0.406	10.3	5.63	OT	CG	N
4.687	119.05	73591	6.00	152.4	3.813	96.9	182	32	2.7	68	486	2162	2.51	63.8	0.437	11.1	5.75	OT	CG	N
4.687	119.05	73597	6.00	152.4	3.751	95.3	245	43	2.4	62	595	2646	2.69	68.4	0.468	11.9	5.75	OT	CG	N
4.687	119.05	73603	6.00	152.4	3.687	93.6	326	57	2.1	54	696	3095	2.88	73.0	0.500	12.7	5.75	OT	CG	N
4.687	119.05	73609	6.00	152.4	3.625	92.1	398	70	2.1	53	830	3693	3.19	80.9	0.531	13.5	6.00	OT	CG	N
4.687	119.05	73615	6.00	152.4	3.563	90.5	511	89	1.9	48	968	4305	3.37	85.7	0.562	14.3	6.00	OT	CG	N
4.687	119.05	73621	6.00	152.4	3.501	88.9	648	113	1.7	44	1110	4938	3.56	90.4	0.593	15.1	6.00	OT	CG	N
4.687	119.05	73627	6.00	152.4	3.437	87.3	818	143	1.6	40	1294	5756	3.75	95.3	0.625	15.9	6.00	OT	CG	N
4.687	119.05	73580	8.00	203.2	3.901	99.1	89	16	4.1	104	364	1620	2.70	68.6	0.393	10.0	6.88	OT	CG	N
4.687	119.05	73586	8.00	203.2	3.875	98.4	100	17	4.0	102	401	1783	2.84	72.2	0.406	10.3	7.00	OT	CG	N
4.687	119.05	73592	8.00	203.2	3.813	96.9	130	23	3.7	95	486	2162	3.17	80.5	0.437	11.1	7.25	OT	CG	N
4.687	119.05	73598	8.00	203.2	3.751	95.3	175	31	3.4	86	595	2646	3.39	86.2	0.468	11.9	7.25	OT	CG	N
4.687	119.05	73604	8.00	203.2	3.687	93.6	233	41	3.0	76	696	3095	3.63	92.1	0.500	12.7	7.25	OT	CG	N
4.687	119.05	73610	8.00	203.2	3.625	92.1	283	50	2.9	75	830	3693	4.05	102.9	0.531	13.5	7.63	OT	CG	N
4.687	119.05	73616	8.00	203.2	3.563	90.5	363	64	2.7	68	968	4305	4.29	108.8	0.562	14.3	7.63	OT	CG	N
4.687	119.05	73622	8.00	203																



1-800-237-5225
1-213-749-1466
 Fax (213)749-3802
 www.centuryspring.com

O.D.		CENTURY STOCK NUMBER	FREE LENGTH		I.D.		RATE		SUGG. MAX. DEFL.		SUGG. MAX. LOAD		SOLID LENGTH		WIRE DIA.		TOTAL COILS	MAT'L	E N D S	F N I S H
Inches	mm		Inches	mm	Inches	mm	Lbs./In.	N/mm	Inches	mm	Lbs.	N	Inches	mm	Inches	mm				
4.906	124.61	73643	14.0	355.6	3.906	99.2	108	19	6.2	157	667	2965	5.86	148.9	0.500	12.7	11.7	OT	CG	N
4.906	124.61	73649	14.0	355.6	3.844	97.6	140	25	5.7	144	796	3539	6.24	158.4	0.531	13.5	11.7	OT	CG	N
4.906	124.61	73655	14.0	355.6	3.782	96.1	175	31	5.3	135	928	4126	6.74	171.2	0.562	14.3	12.0	OT	CG	N
4.906	124.61	73661	14.0	355.6	3.720	94.5	222	39	4.8	122	1064	4734	7.10	180.4	0.593	15.1	12.0	OT	CG	N
4.906	124.61	73667	14.0	355.6	3.656	92.9	273	48	4.5	115	1241	5520	7.65	194.3	0.625	15.9	12.2	OT	CG	N
4.906	124.61	73638	16.0	406.4	3.970	100.8	70	12	8.1	207	570	2534	6.21	157.7	0.468	11.9	13.3	OT	CG	N
4.906	124.61	73644	16.0	406.4	3.906	99.2	93	16	7.2	182	667	2965	6.65	168.8	0.500	12.7	13.3	OT	CG	N
4.906	124.61	73650	16.0	406.4	3.844	97.6	121	21	6.6	167	796	3539	7.05	179.1	0.531	13.5	13.3	OT	CG	N
4.906	124.61	73656	16.0	406.4	3.782	96.1	152	27	6.1	155	928	4126	7.59	192.8	0.562	14.3	13.5	OT	CG	N
4.906	124.61	73662	16.0	406.4	3.720	94.5	193	34	5.5	140	1064	4734	7.99	203.0	0.593	15.1	13.5	OT	CG	N
4.906	124.61	73668	16.0	406.4	3.656	92.9	238	42	5.2	132	1241	5520	8.59	218.2	0.625	15.9	13.7	OT	CG	N
5.000	127.00	4053	5.00	127.0	3.000	76.2	11230	1967	.4	10	4200	18690	4.00	101.6	1.000	25.4	4.00	HD	CG	N
5.000	127.00	4083	8.00	203.2	3.812	96.8	465	81	2.0	51	934	4155	3.86	98.1	0.594	15.1	6.50	HD	CG	N
5.000	127.00	4031	12.0	304.8	4.000	101.6	123	22	4.7	120	582	2589	5.00	127.0	0.500	12.7	10.0	SPR	CG	N
5.000	127.00	4088	12.0	304.8	3.124	79.3	2767	485	1.3	33	3600	16000	7.50	190.6	0.938	23.8	8.00	HD	CG	N
5.250	133.35	4022-A	4.00	101.6	4.926	125.1	4.1	.73	3.4	87	14	63	.56	14.2	0.162	4.1	3.50	SST	CG	N
5.500	139.70	4036	12.0	304.8	4.438	112.7	162	28	3.9	100	635	2824	4.12	104.5	0.531	13.5	7.75	SPR	CG	N
5.500	139.70	4000-A	18.8	476.3	4.500	114.3	78	14	6.8	174	532	2365	5.63	142.9	0.500	12.7	11.3	SPR	CG	N
5.750	146.05	4097	12.0	304.8	4.000	101.6	1818	318	1.4	36	2550	11350	5.25	133.4	0.875	22.2	6.00	HD	CG	N
6.000	152.40	4034	3.50	88.9	4.626	117.5	2135	374	.6	15	1220	5430	2.06	52.3	0.687	17.4	3.00	SPR	CG	N
6.000	152.40	4094	8.75	222.3	4.250	108.0	1669	292	1.5	38	2440	10860	5.03	127.8	0.875	22.2	5.75	HD	CG	N
6.000	152.40	4091	24.0	609.6	4.624	117.4	175	31	7	178	1210	5380	9.80	249.0	0.688	17.5	14.3	HD	CG	N
6.060	153.92	4099-A	17.0	431.8	5.490	139.4	4.9	.86	13	338	65	291	3.71	94.1	0.285	7.2	12.0	HD	C	GI
6.125	155.58	4078	14.0	355.6	5.687	144.4	3.5	.61	12	317	44	193	1.53	38.9	0.218	5.6	6.00	SST	C	N
6.250	158.75	4099-B	5.38	136.5	5.250	133.4	291	51	1.8	46	529	2354	1.81	46.1	0.500	12.7	3.63	OT	CG	N
6.250	158.75	4095	12.0	304.8	4.750	120.7	547	96	2.7	69	1500	6670	5.25	133.4	0.750	19.1	7.00	HD	CG	N
6.500	165.10	4089	5.00	127.0	4.500	114.3	4320	757	.8	20	3460	15400	4.00	101.6	1.000	25.4	4.00	HD	CG	N
6.500	165.10	4098	8.00	203.2	4.500	114.3	2033	356	1.6	41	3360	14950	6.25	158.8	1.000	25.4	6.25	HD	CG	N
6.500	165.10	4092	10.0	254.0	5.376	136.6	211	37	3.0	76	632	2811	2.95	74.9	0.562	14.3	5.25	HD	CG	N
7.250	184.15	4024-B	13.0	330.2	5.500	139.7	591	104	3.5	89	2060	9170	6.56	166.7	0.875	22.2	7.50	SPR	CG	N
7.250	184.15	4099	29.0	736.6	6.126	155.6	34	6.0	17	422	569	2532	8.99	228.4	0.562	14.3	16.0	HD	CG	N
7.500	190.50	4022-C	6.50	165.1	6.000	152.4	370	65	2.0	51	739	3289	4.50	114.3	0.750	19.1	6.00	HD	CG	N
7.750	196.85	4044	10.0	254.0	6.938	176.2	39	6.9	5.6	141	219	975	1.83	46.4	0.406	10.3	4.50	SPR	CG	N
8.000	203.20	4024	10.0	254.0	6.250	158.8	717	126	2.6	66	1880	8360	4.59	116.7	0.875	22.2	5.25	SPR	CG	N
9.000	228.60	4027	32.0	812.8	7.876	200.1	28	4.9	16	418	462	2055	5.90	149.9	0.562	14.3	10.5	SPR	CG	N
9.250	234.95	4024-A	15.8	400.1	6.626	168.3	2004	351	2.7	69	5370	23890	8.20	208.3	1.312	33.3	6.25	HD	CG	N

MATERIAL: MW - Music Wire
 SPR - Spring Steel
 HD - Hard Drawn
 OT - Oil Tempered

SST - Stainless Steel
 BC - Beryllium Copper
 PB - Phosphor Bronze

ENDS: C - Closed
 G - Ground
 O - Open

FINISH: Z - Zinc
 BO - Black Oxide
 GI - Gold Iridite
 N - None



LONG LENGTH COMPRESSION SPRINGS

The primary purpose of the 20" long stainless and 36" long carbon steel spring bodies found in the following tables is to offer our customers a means for creating a desired custom length and/or spring compression travel for a given load. Once cut, the end coils may be bent back to touch the previous coil to create a squared end.

The spring rate constant (lbs./in.) can be determined for any cut length by simply dividing the final length, in inches, into the appropriate rate-inch value listed for the spring body. The spring rate is merely the pounds it takes to compress a spring each inch, i.e., if the rate = 5 lbs. per inch, it would take 5 pounds to compress it one inch, 10 pounds to compress it 2 inches, 15 pounds for 3 inches, etc..

LONG LENGTH COMPRESSION SPRINGS

STAINLESS STEEL (302) 20 INCH LENGTHS

CENTURY STOCK NUMBER	O.D.		I.D.		WIRE DIA.		PITCH		RATE-INCH		SUGG. MAX LOAD		SOLID LGTH PER	
	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Lbs.	N	Lbs.	N	Lbs.	N
ST2-13	0.125	3.18	0.099	3	0.013	0.33	.042	1	1.1	4.9	.8	3.6	.32	8.1
ST2-15	0.125	3.18	0.095	2	0.015	0.38	.040	1	1.9	8.5	1.2	5.3	.39	9.9
ST2-17	0.125	3.18	0.091	2	0.017	0.43	.035	1	3.0	13	1.8	8.0	.49	12
ST2-20	0.125	3.18	0.085	2	0.020	0.51	.033	1	5.8	26	2.8	12	.61	15
ST3-15	0.187	4.75	0.157	4	0.015	0.38	.067	2	1.0	4.4	.8	3.6	.21	5.3
ST3-17	0.187	4.75	0.153	4	0.017	0.43	.066	2	1.4	6.2	1.2	5.3	.28	7.1
ST3-20	0.187	4.75	0.147	4	0.020	0.51	.066	2	2.9	13	1.9	8.5	.32	8.1
ST3-26	0.187	4.75	0.135	3	0.026	0.66	.052	1	7.3	32	4	18	.51	13
ST4-15	0.250	6.35	0.220	6	0.015	0.38	.125	3	.60	2.7	6.4	28	.13	3.3
ST4-17	0.250	6.35	0.216	5	0.017	0.43	.117	3	1.0	4.4	.9	4.0	.16	4.1
ST4-20	0.250	6.35	0.210	5	0.020	0.51	.098	2	1.6	7.1	1.4	6.2	.22	5.6
ST4-26	0.250	6.35	0.198	5	0.026	0.66	.080	2	4.2	19	3.1	14	.34	8.6
ST4-32	0.250	6.35	0.186	5	0.032	0.81	.070	2	10	46	5.5	24	.42	11
ST5-20	0.312	7.92	0.272	7	0.020	0.51	.150	4	1.2	5.3	1.2	5.3	.15	3.8
ST5-26	0.312	7.92	0.260	7	0.026	0.66	.114	3	2.9	13	2.5	11	.25	6.4
ST5-32	0.312	7.92	0.248	6	0.032	0.81	.095	2	7.0	31	4.5	20	.31	7.9
ST5-41	0.312	7.92	0.230	6	0.041	1.04	.080	2	15	66	8.9	40	.53	13
ST6-32	0.375	9.53	0.311	8	0.032	0.81	.130	3	4.4	20	3.8	17	.27	6.9
ST6-41	0.375	9.53	0.293	7	0.041	1.04	.111	3	11	49	7.5	33	.39	9.9
ST6-54	0.375	9.53	0.267	7	0.054	1.37	.095	2	32	142	16	71	.60	15
ST7-41	0.438	11.13	0.356	9	0.041	1.04	.130	3	7.6	34	6.5	29	.34	8.6
ST7-54	0.438	11.13	0.330	8	0.054	1.37	.117	3	23	102	14	62	.49	12
ST8-54	0.500	12.70	0.392	10	0.054	1.37	.142	4	18	80	12	53	.41	10
ST8-72	0.500	12.70	0.356	9	0.072	1.83	.133	3	61	271	27	120	.57	14
ST9-41	0.562	14.27	0.480	12	0.041	1.04	.146	4	3.8	17	5	22	.31	7.9
ST9-54	0.562	14.27	0.454	12	0.054	1.37	.166	4	14	62	11	49	.36	9.1
ST9-72	0.562	14.27	0.418	11	0.072	1.83	.142	4	44	196	24	107	.54	14
ST9-91	0.562	14.27	0.380	10	0.091	2.31	.142	4	128	569	46	205	.67	17
ST10-72	0.625	15.88	0.481	12	0.072	1.83	.166	4	35	156	22	98	.47	12
ST10-91	0.625	15.88	0.443	11	0.091	2.31	.160	4	99	440	42	187	.61	15
ST12-91	0.750	19.05	0.568	14	0.091	2.31	.200	5	66	294	35	156	.50	13

AVAILABLE FOR IMMEDIATE SHIPMENT



LONG LENGTH COMPRESSION SPRINGS

LONG LENGTH COMPRESSION SPRINGS

CARBON STEEL (ASTM A227) 36 INCH LENGTHS

CENTURY STOCK NUMBER	O.D.		I.D.		WIRE DIA.		PITCH		RATE-INCH		SUGG. MAX LOAD		SOLID LGTH PER	
	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Lbs.	N	Lbs.	N	Lbs.	N
R-1	0.094	2.39	0.068	2	0.013	0.33	.028	1	2.2	9.8	1	4.4	.48	12
R-2	0.125	3.18	0.097	2	0.014	0.36	.039	1	1.6	7.1	.9	4.0	.38	9.7
R-3	0.125	3.18	0.089	2	0.018	0.46	.037	1	4.6	12	1.9	6.2	.45	11
R-4	0.125	3.18	0.079	2	0.023	0.58	.036	1	13.7	62	3.8	17	.65	17
R-5	0.187	4.75	0.151	4	0.018	0.46	.063	2	2.0	8.9	1.4	6.2	.30	7.6
R-6	0.187	4.75	0.131	3	0.028	0.71	.063	2	13.8	62	5	22	.46	12
R-7	0.250	6.35	0.204	5	0.023	0.58	.083	2	2.9	13	2	8.9	.30	7.6
R-8	0.250	6.35	0.180	5	0.035	0.89	.072	2	15.6	71	7	31	.50	13
R-9	0.312	7.92	0.230	6	0.041	1.04	.091	2	18.6	85	8	36	.47	12
R-10	0.312	7.92	0.217	6	0.048	1.21	.086	2	35.8	160	12	53	.57	14
R-11	0.375	9.53	0.305	8	0.035	0.88	.130	3	7.1	31	5	22	.30	7.6
R-12	0.438	11.13	0.343	9	0.048	1.21	.130	3	16.7	75	9	40	.40	10
R-13	0.500	12.70	0.405	10	0.048	1.21	.167	4	13.8	68	8	36	.39	9.9
R-14	0.500	12.70	0.392	10	0.054	1.37	.151	4	20.9	98	12	53	.39	9.9
R-15	0.500	12.70	0.375	10	0.063	1.59	.139	4	38.0	173	17	76	.48	12
R-15-A	0.562	14.27	0.467	12	0.048	1.21	.132	3	7.4	33	4.7	31	.39	9.9
R-16	0.562	14.27	0.437	11	0.063	1.59	.176	4	32.0	147	15	67	.39	9.9
R-17	0.562	14.27	0.402	10	0.080	2.03	.157	4	83.0	400	30	133	.55	14
R-18	0.625	15.88	0.501	13	0.062	1.57	.204	5	24.5	120	14	62	.35	8.9
R-19	0.625	15.88	0.481	12	0.072	1.83	.181	5	41.5	200	21	93	.44	11
R-20	0.625	15.88	0.442	11	0.092	2.32	.175	4	120.0	574	40	178	.57	14
R-21	0.750	19.05	0.590	15	0.080	2.03	.234	6	46.0	222	23	102	.39	9.9
R-22	0.750	19.05	0.540	14	0.105	2.67	.210	5	137.0	681	49	218	.55	14
R-23	0.875	22.23	0.715	18	0.080	2.03	.300	8	35.2	169	20	89	.33	8.4
R-24	1.000	25.40	0.817	21	0.092	2.32	.317	8	43.9	209	26	116	.35	8.9
R-25	1.000	25.40	0.759	19	0.121	3.06	.287	7	131.0	645	55	245	.49	12
R-26	1.000	25.40	0.730	19	0.135	3.43	.272	7	201.6	1032	75	334	.56	14
R-27	1.125	28.58	0.914	23	0.106	2.68	.382	10	65.5	311	34	151	.35	8.9
R-27-A	1.188	30.18	0.738	19	0.225	5.72	.337	9	1404	7980	252	1121	.74	19
R-28	1.250	31.75	1.009	26	0.121	3.06	.375	10	75.6	391	44	196	.40	10
R-29	1.250	31.75	0.954	24	0.148	3.76	.348	9	180	934	78	347	.51	13
R-29-A	1.375	34.93	1.079	27	0.148	3.76	.340	9	127	663	71	316	.52	13
R-30	1.500	38.10	1.176	30	0.162	4.11	.422	11	175	925	84	374	.48	12
R-31	1.750	44.45	1.376	35	0.187	4.75	.470	12	216	1183	108	480	.51	13

AVAILABLE FOR IMMEDIATE SHIPMENT