METGAL

ELECTRONICS BENCH TOOL SOLUTIONS



HAND SOLDERING,

DESOLDERING AND

REWORK

CONVECTION

REWORK

FUME

EXTRACTION

FLUID

DISPENSING
















HAND SOLDERING

CONVECTION REWORK

TECHNOLOGICAL ADVANTAGES WITH BEST-IN-CLASS PERFORMANCE.



CONTACT US

NORTH AMERICA
OK INTERNATIONAL, INC.
12151 MONARCH STREET
GARDEN GROVE, CA 92841
TEL: 1-714-799-9910
FAX: 1-714-799-9533
INFO@OKINTERNATIONAL.COM

EUROPE

OK INTERNATIONAL LTD.
EAGLE CLOSE, CHANDLERS FORD
HAMPSHIRE, SO53 4NF, U.K.
TEL: +44 (0) 23 8048 9100
FAX: +44 (0) 23 8048 9109
EUROPE@OKINTERNATIONAL.COM

GERMAN SALES SUPPORT
TEL: +49 (0)6101 522 7470
FAX: +49 (0)6101 522 7479
D-INFO@OKINTERNATIONAL.COM

French Sales Support
Tel: +33 (0)1 76 71 04 03
Fax: +33 (0)1 70 71 21 50
FR-INFO@OKINTERNATIONAL.COM

ASIA

OK International
4 Floor West, 1st Building, Tingwe
Industrial Park, 6 Liufang Road
Baocheng 67th Area, Baoan
District Shenzhen,
Guangdong, 518101
PRC
Tel: +86-138-2318-7408

Tel: +86-138-2318-7408 CHINA@OKINTERNATIONAL.COM

SALES SUPPORT
JAPAN
SALES: +81-198-22-7928
SERVICE: +81-03-4520-9629
FAX: +81-03-6745-1439









FUME EXTRACTION

FLUID DISPENSING

TABLE OF CONTENT

Hand Soldering, Desoldering and Rework	2-29
MX-5200 Series	4-7
Multi Function Rework Series	8-13
Production Soldering Series	14-15
Tips and Cartridges	
Convection Rework	30-49
Advanced Package Rework Systems	32-37
Nozzles and Accessories	
Modular Rework System	
HandHeld Series	
Fume Extraction	50-53
Portable Series	50
Multi Function Series	51
Arms and Accessories	
Tip Extraction Series	
Fluid Dispensing	54-57
Dispensers / Controllers	
Dispensing Tips	
Dispensing Consumables	
A	



Visit www.metcal.com to download this catalog, and check out our Applications section and library of videos.

We are committed to understanding the product needs of our customers, and supply professional grade products that are innovative, reliable, price competitive and easy to use.



Metcal is part of the OK International family and provides expert product support and responsive customer service, with localization to meet regional market needs.

SERVING THE ELECTRONICS ASSEMBLY INDUSTRY FOR OVER 30 YEARS

Hand Soldering, Desoldering &

Single Port



PS-900 Production Soldering





MFR-1100 Series
Soldering / Desoldering / Rework





MFR-1300 Series
Soldering / Desoldering







TIO

SmartHeat® Technology

OK International is the original supplier of SmartHeat® Soldering Technology. SmartHeat® senses the exact thermal requirement for each solder joint and responds by delivering the precise amount of thermal energy required to create a reliable connection.

The result is a high degree of control without resorting to higher tip idle temperatures required by conventional heater process technologies. Consequently, the risk of component and board damage is minimized. This is especially important with the greater thermal demands required by lead-free applications.



Rework Systems Overview

Dual Port Simultaneous



Soldering / Rework




REWORK



MX-5200 Series Soldering / Desoldering / Rework



S Y S T E M S




SmartHeat® Soldering Technology = Variable Power / Fixed Temperature

- ▶ SmartHeat® tips and cartridges sense the load and instantly deliver the right amount of heat directly to the solder joint.
- The required solder joint temperature drives the heating process, as opposed to the idle tip temperature setting (as in a conventional iron).
- Operates at lower and safer temperatures. Power is delivered in proportion to the load. SmartHeat® technology eliminates overshoot.
- No calibration required saves money and eliminates system down-time.

Watch SmartHeat® Video on www.metcal.com

Soldering, Desoldering & Rework Systems




For two users or single user with dual applications. The MX-5200 can be operated with two hand-pieces dynamically sharing the 80 watts output power based on demand adding even more application flexibility and speed.

Fast time-to-recovery. Delivering increased production rates and throughput. No matter the application. The challenges of high mass components, multilayered boards and lead-free solders are seamlessly tackled by the MX-5200 super-charged power supply.

SmartHeat process control. Our Technology built-in every Metcal System means that soldering and rework are always performed at safe, controlled temperatures. Metcal users know that moderate fixed temperatures, where power is varied, provide the best assurance for a well controlled soldering and rework process.

TipSaver™ Workstand improves tip life as well as operator ergonomics. This "Auto-Sleep" Workstand reduces the power to the hand-piece when it is placed in the Metcal TipSaver™ Workstand. Reduction in power will substantially decrease tip oxidation, a major cause of reduced tip life.



ESD safe and features incoming AC ground monitoring circuitry. This AC (mains) ground monitor detects power line ground failures and immediately alerts the operator and shuts down the system. Only after the power line has been restored, can the MX-5000 be restarted and soldering operations can be resumed.

Built-in power indication meter with digital display and bar graph that dynamically provides the operator with feedback on the status of the soldering operation. Whether using a large mass rework tip for QFPs or a fine-point soldering tip, the power indication meter is a valuable resource for making consistent, acceptable solder joints.



Four mode indicators:

Ready Mode: The hand-piece is removed from the workstand, ready for soldering or rework.

Power Mode: The hand-piece's tip is in contact with the load. The power indication meter provides graphical and numeric feedback on the system power output.

Sleep Mode (Programmable sleep from 10 to 120min): The hand-piece is at rest in the workstand; power is reduced to the hand-piece.

Powersave Mode: Power to the hand-piece is shut off. This programmable feature allows an operator to set the desired time to cut off power to the hand-piece.

SYSTEMS CONFIGURATION

PART	MX-PS5200		Hand-	and-pieces		TipSaver™ Workstands		
NUMBER	Power Supply	MX-H1-AV	MX-H2-UF	MX-PTZ	MX-DS1	MX-W1AV	MX-W4PT	MX-W5DS
MX-5210	~	~				~		
MX-5211	~	~ ~				~ ~		
MX-5220	~		~			~		
MX-5241	~	~		~		~	~	
MX-5250	~				~			~
MX-5251	~	~			~	~		~

SYSTEMS WITH ONE HAND-PIECE

SYSTEMS WITH TWO HAND-PIECES



STTC Series and

SMTC Series





Soldering cartridges: UFTC cartridges featuring small tip geometries and low mass, suited for small part soldering.







Soldering, Desoldering & Rework Systems

HAND-PIECES & CARTRIDGES

The MX-5200 Series offers users a choice of hand-pieces to meet the customer's application needs. Each hand-piece has its own range of cartridges with many choices available for tip geometry and temperature.









MX-H2-UF Metcal UltraFine™

Hand-pieces

MX-H1-AV Metcal Advanced™ Hand-piece

Hand-piece

MX-PTZ Metcal Precision Tweezer Hand-piece

MX-DS1 Metcal Desoldering Hand-piece





UFTC







SMTC





STDC



Note: The hand-pieces shown above are backward compatible with the MX-5000 and MX-500 systems. Cartridges are not included with the hand-pieces.

STTC	Soldering Cartridges	See Series on pages 16-17
UFTC	Ultra Fine Soldering Cartridges	See Series on page 18
SMTC	Rework Cartridges	See Series on pages 19-20
PTTC / TATC	Tweezer / Talon Cartridges	See Series on page 21
STDC	Desoldering Cartridges	See Series on page 22

STTC

STTC	Soldering Cartridges	See Series on pages 16-17	
UFTC	Ultra Fine Soldering Cartridges	See Series on page 18	4
SMTC	Rework Cartridges	See Series on pages 19-20	-
PTTC / TATC	Tweezer / Talon Cartridges	See Series on page 21	5
STDC	Desoldering Cartridges	See Series on page 22	3
	-		

	Hand-pieces and Grips
MX-H1-AV	Metcal Advanced™ Hand-piece with cord, soldering and rework, three grips included
MX-H1GR 1	Grip Metcal Advanced™ Hand-piece with black sleeve in ring pattern
MX-H1GS 3	Grip Metcal Advanced™ Hand-piece with black scallop pattern
MX-H1GKG 2	Grip Metcal Advanced™ Hand-piece with green knob pattern
MX-H2-UF	Metcal UltraFine™ Hand-piece with cord, fine soldering, three grips included
MX-H2GR 5	Grip Metcal UltraFine™ Hand-piece with black sleeve in ring pattern
MX-H2GRS 4	Short grip Metcal UltraFine™ Hand-piece with black sleeve in ring pattern
MX-H2GS	Grip Metcal UltraFine™ Hand-piece with black sleeve in scallop pattern
MX-H2GKG	Grip Metcal UltraFine™ Hand-piece with green sleeve in knob pattern
MX-PTZ	Metcal Precision Tweezers, SMD rework
MX-DS1	Metcal Desoldering Hand-piece
MX-RM8E	Metcal Desoldering Hand-piece Cord for MX-DS1
MX-RM5E	Standard Robotic cable (1.83m / 6ft) with connector for Soldering/Rework cartridges
MX-RM6E	Metcal Soldering/Rework Hand-piece for long reach cartridge access

Soldering, Desoldering & Rework Systems

WORKSTANDS & ACCESSORIES

	Workstands and Accessories
MX-W1AV	Metcal TipSaver™ Workstand, for Metcal Advanced™ and UltraFine™ Hand-pieces
MX-W1CR	Cradle for TipSaver™ Workstand, Advanced™ and UltraFine™ Hand-pieces, incl. knobs
MX-W4PT	Metcal TipSaver™ Workstand, for MX-PTZ Hand-piece
MX-W4CR	Cradle for Metcal TipSaver™ Workstand, MX-PTZ Hand-piece, includes knobs
MX-W5DS	Metcal TipSaver™ Workstand, for MX-DS1 Hand-piece
MX-W5CR	Cradle for Metcal TipSaver™ Workstand, MX-DS1 Hand-piece, includes knobs
AC-Y10	Yellow sponge, pack of 10
AC-BP	Brass pad, pack of 10
AC-BRUSH-P	Soft Brass Brush, pack of 6
MX-CP1	Cartridge removal pad
Note: cartridges not in	ncluded with hand-pieces
	Accessories for MX-DS1 Desoldering Hand-piece
MX-DCF1	Chamber Liners (pack of 15) and Filters (pack of 6)
MX-DCF1L	Chamber Liners (pack of 40)
MX-DCF1F	Filters (pack of 20)
AC-TC-P	Desolder Tip Cleaner
AC-CB1-P	Desolder Chamber Cleaning Brush (pack of 25)
AC-CB2-P	Tube Cleaning Brush (pack of 6)
MX-DSL2	Seal Cartridge
MX-DSB	Swivel Connector
MX-DLA	Desolder Gun Latch Adjustment (pack of 10)
MX-DMK1	Maintenance Kit
MX-DAH4	ESD air hose for MX-DS1 Desoldering Hand-piece
MX-DSL1	Seal Chamber
MX-DVC1	Venturi Cartridge
MX-DAR1	Air Regulator and Filter

Note: Users of the MX-500 System that have either an MX-RM3E Hand-piece or an MX-TALON Tweezer Hand-piece can still use these hand-pieces with the MX-5200 System. However, for improved operator comfort and ergonomics, the new Metcal Advanced™ Hand-piece (STTC and SMTC cartridges) and the MX-PTZ Precision Tweezers are highly recommended.



Through hole desoldering with the MX-DS1 hand-piece.

U	UPGRADE KITS GUIDE: HAND-PIECE AND WORKSTAND								
PART		Hand-	pieces		'	Workstands	5		
NUMBER	MX-H1- AV	MX-H2- UF	MX-PTZ Precision Tweezers	MX-DS1 Desoldering	MX-W1AV	MX-W4PT	MX- W5DS		
MX-UK1	~				~				
MX-UK2		~			~				
MX-UK4			~			~			
MX-UK5				>			~		

Upgrade kits include a hand-piece and a workstand. Upgrade kits are a recommended option when adding a hand-piece to ensure that the matching Auto-Sleep Workstand is used.


TECHNICAL SPECIFICATIONS



BGA pad cleaning with SMTC blade tip cartridge. See full range on page 20.

MFR-2200 Series Dual Output

Simultaneous Soldering & Rework Systems



The MFR-2200 Series features dual output capability allowing users to select operation of one hand-piece or two hand-pieces **simultaneously**.

The MFR-2200 Systems below offer a choice of three hand-pieces, however two additional hand-pieces including the desoldering option are also available as upgrade kits (see pages 11 & 13).







Systems	MFR-PS2200 Power Supply	MFR-H1-SC Soldering Cartridge Hand-piece	MFR-H2-ST Soldering Tip Hand-piece	MFR-H4-TW Tweezer Hand-piece	WS1 Universal Soldering Workstand	MFR-WSPT Tweezer Workstand
Picture Reference		1	2	3		
MFR-2210	1	1			1	
MFR-2220	1		1		1	
MFR-2240	1			1		1
MFR-2211	1	2			2	
MFR-2222	1		2		2	
MFR-2241	1	1		1	1	1









MFR-1100 Series Single Output

Soldering & Rework Systems



The MFR-1100 Single Output Series is designed to minimize training investment, maximize application solutions and increase productivity.

This Series is compact and **versatile**. It can be used with either a soldering tip, cartridge or tweezers hand-piece. A desoldering option is also available as an upgrade kit (see pages 11 & 13).



Systems	MFR-PS1100 Power Supply	MFR-H1-SC Soldering Cartridge Hand-piece	MFR-H2-ST Soldering Tip Hand-piece	MFR-H4-TW Tweezer Hand-piece	MFR-H6-SSC SSC Cartridge Hand-piece	WS1 Soldering Workstand	MFR-WSPT Tweezer Workstand	WS2 Soldering Workstand
Picture Reference		1	2	3	4	5		6
MFR-1110	1	1				1		
MFR-1120	1		1			1		
MFR-1140	1			1			1	
MFR-1160	1				1			1
MFR-1161	1	1			1	1		1

Note: The MFR-1160 replaces the Metcal SP200 Soldering System. The MFR-H6-SSC hand-piece accepts the same SSC cartridges.









MFR-1100 & MFR-2200 Series

Soldering & Rework Systems



Systems from both MFR-2200 and MFR-1100 series can be locked together for increased flexibility.



MFR-2200: Three position switch. Select left, right or center (both ports operational) to power hand-pieces

Key Features & Benefits

- SmartHeat® Technology provides exceptional power for high thermal demand applications
- Single or Dual simultaneous outputs allow for single or dual hand-piece use
- Five hand-pieces available for increased application solutions for soldering, desoldering (upgrade kit) and rework on one system
- Each hand-piece has a comprehensive range of cartridges or tips for maximum flexibility
- Hand-pieces are ergonomic for operator safety and comfort

Other Accessories Available:

MFR-CA2	Coil Assembly for Tip Hand-piece (MFR-H2-ST)
WS1G	Auto-sleep Workstand, Green
MFR-PM70	Power Meter
AC-CP2	Cartridge / Tip Removal Pad
AC-BP	Brass Pad (for Workstand) - Pack of 10

Technical Specifications

Power Supply	MFR-1100	MFR-2200
Ambient Operating Temperature	10 - 40°C (50°F - 104°F)	10 - 40°C (50°F - 104°F)
Maximum Enclosure Temperature	55°C (131°F)	55°C (131°F)
Input Line Voltage	100 - 240 VAC	100 - 240 VAC
Input Line Frequency	50/60 Hz grounded circuit	50/60 Hz grounded circuit
Power Consumption	70 Watts maximum	130 Watts maximum
Output Power	60 Watts at 22°C	60 Watts at 22°C per output (2 outputs)
Output Frequency	450 KHz	450 KHz
Power Cord (3-wire)	183 cm 18/3 SJT	183 cm 18/3 SJT
Dimensions (approx.) W x D x H	90mm (3.5") x 142mm (5.6")	170mm (7") x 200mm (8")
	x 197mm (7.8")	x 152.5mm (6")
Weight	2.3kg (5.05 lbs)	2.97 kg (6.55 lbs)
Surface Resistivity	10 ⁵ -10 ⁹ Ohms	10 ⁵ -10 ⁹ Ohms
Certification / Marking	cTUVus, CE	cTUVus, CE

Soldering Handle and Coil Assembly

Tip-to-Ground Potential	<2 mV RMS	< 2 mV RMS
Tip-to-Ground Resistance	<2 ohms	<2 ohms
Idle Temperature Repeatability	± 1.1°C (2°F) in still air	± 1.1°C (2°F) in still air
Handle Cord Assembly Length	122 cm - burn proof, ESD safe	122 cm – burn proof, ESD safe
Connector	8-pin circular DIN	8-pin circular DIN
Workstand W x D x H	100 mm (4") x 200 mm (8")	100 mm (4") x 200 mm (8")
	x 100 mm (4")	x 100 mm (4")
Workstand Weight	0.69 kg (1.51 lbs)	0.69 kg (1.51 lbs)

MFR-1150 Single Output Soldering & Desoldering Systems with Venturi

The MFR-1150 Desolder System with Venturi Workstand provides a compact and easy shop air option.

Key Features & Benefits

- Venturi workstand
- 2 in 1 Desolder hand-piece
- MFR-H5-DS & MFR-WSDSX are compatible for use with all MFR systems (available under MFR-UK5 upgrade kit)
- Uses DxP desolder cartridges and replaceable coil assembly (MFR-HDCA)

Part No.	Description
MFR-1150	Complete System
Includes:	
MFR-PS1100	Power Supply
MFR-H5-DS	Desolder hand-piece
MFR-WSDSX	Workstand with venturi box for desolder hand-piece
MFR-FTKIT	Fittings and air hose kit
AC-TC	Tip cleaner





Technical Specifications

	MFR-PS1100 Power Supply
Input Line Voltage	100-240 VAC
Input Line Frequency	50/60Hz
Power Consumption	65 Watts max.
Output Power	60 Watts Max (RF SmartHeat® Power)
Output Frequency	450 KHz
Dimensions W x D x H	90mm x 200mm x 152.5mm (3.5" x 8" x 6")
Output Frequency	450 KHz

	MFR-1150 System
Idle Tip temperature stability	+/- 1.1°C (2°F) in still air
Ambient Operating Temperature	10 - 40°C (50 - 104°F)
Maximum Enclosure Temperature	55°C (131°F)
Tip to ground Potential	<2mV
Tip to ground resistance	<2 Ohms
Surface resistivity	10 ⁵ – 10 ⁹ Ohm
Approvals	cTUVus, CE



Collection chamber replacement



Remove grip for Pencil config.

MFR-H5-DS Desolder Hand-piece



MFR-UK5 Upgrade Kit
Compatible with all MFR
Series Power Supplies

	min it ito Do Doodiadi itania piddo
Power Cord (3-wire)	183cm (72")
Solder Hand-piece cable length	152 cm (60"), burn proof, ESD safe
Hand piece connector	8 pin power connector
	MFR-WSDSX Workstand
Input voltage	24V
Intput power	15W
Workstand dimensions	100mm x 200mm x 140mm (4" x 8" x 5.5")
Noise level	< 55 dB
Recommended Air pressure input	550kPa (80PSI) - Shop air only
Vacuum suction force	0.85 bar (25" Hg)

MFR-1300 Dual Switchable Output

Soldering & Desoldering Systems with Internal Air

The MFR-1300 Desoldering and Rework System features a innovative desoldering hand-piece and a power supply with an **internal pump** providing 0.7 bar of vacuum suction force making through-hole desoldering easy.

Key Features & Benefits

- Self-contained powerful pump
- 2 in 1 ergonomic and flexible hand-piece
- ▶ Collection chamber with increased capacity
- Quick and easy change collection chamber
- Dual switchable output
- ▶ Powered by Smartheat® Technology
- Compatible with previous MFR Desolder range



Part No.	Description
MFR-1350	Desolder System with Internal Pump*
MFR-1351	Solder / Desolder System with Internal Pump**
Includes:	
MFR-PS1300	Power Supply
MFR-H5-DS*	Desolder hand-piece
MFR-H1-SC*	Solder Cartridge hand-piece
MFR-WSDSU*	Workstand for Desolder hand-piece
WS1*	Workstand for Solder hand-piece





Technical Specifications

	MFR-1350/51
Input Line Voltage	100-240 VAC
Input Line Frequency	50/60Hz
Power Consumption	110 Watts max. (Power Supply MFR-PS1300)
Output Power	60 Watts Max (RF SmartHeat® Power)
Output Frequency	450 KHz
Idle Tip temperature stability	+/- 1.1°C (2°F) in still air
Ambient Operating Temperature	10 - 40°C (50 - 104°F)
Maximum Enclosure Temperature	55°C (131°F)
Noise level	< 55 dB
Vacuum suction force	0.7 bar (21in Hg at Vacuum pump at sea level)
Power Cord (3-wire)	183cm (72")
Desolder Hand-piece cable length	152 cm (60"), burn proof, ESD safe
Solder Hand-piece cable length	122 cm (48"), burn proof, ESD safe
Hand piece connector	8 pin power connector
Tip to ground Potential	<2mV
Tip to ground resistance	<2 Ohms
Surface Resistivity	10 ⁵ – 10 ⁹ Ohms
Approvals	cTUVus, CE
Dimensions (approx.) W x D x H	170mm x 200mm x 152.5mm (7" x 8" x 6")
Workstand dimensions	100mm x 200mm x 100mm (4" x 8" x 4")



Pencil



Pistol

Accessories and Spare Parts For MFR and PS Series











Hand-pieces an	d replacement coils
PS-HC3	Soldering Handle with PS-CA3 Coil Assembly (PS-900)
PS-H3 1	Soldering Handle without Coil Assembly (PS-900)
PS-CA3 2	Coil Assembly for PS-HC3 / PS-H3 Hand-piece (PS-900)
MFR-H1-SC 3	Cartridge Solder / Rework Hand- piece (MFR-1100 & MFR-2200)
MFR-H2-ST 4	Tip Solder Hand-piece (MFR-1100 & MFR-2200)
MFR-CA2	Coil Assembly for MFR-H2-ST Hand- piece (MFR-1100 & MFR-2200)
MFR-H4-TW 5	Precision Tweezer Hand-piece (MFR-1100 & MFR-2200)
MFR-H6-SSC 6	SSC Cartridge Solder Hand-piece (MFR-1100 & MFR-2200)
MFR-H5-DS 7	Desolder Hand-piece
MFR-HSREC	Cartridge Solder / Rework Hand- piece with long cord (1.83m / 6ft)
MFR-HSRLR 8	Cartridge Solder / Rework Hand- piece with long reach access
Workstands	
WS1	Universal Auto Sleep Workstand
WS2	Round Auto Sleep Workstand
WS2-NS 9	Solder Workstand (PS-900)
MFR-WSPT 10	Non Sleeper Precision Tweezer Workstand
MFR-WSDSX 11	Venturi Workstand for Desolder Hand-piece
MFR-WSDSU	Non Sleeper Workstand for Desolder Hand-piece
WS1CB	Solder Rework Cradle Replacement for WS1 Workstand
WS2CB	Solder Rework Cradle Replacement for WS2 Workstand
MFR-WSDSCB	Replacement cradle for all MFR Desolder Workstands
Unarada Kite	

Upgrade Kits	
MFR-UK1	Solder Cartridge Hand-piece (MFR-H1-
	SC) and Workstand (WS1)
MFR-UK2	Solder Tip Hand-piece (MFR-H2-ST) and
	Workstand (WS1)
MFR-UK4	Tweezer Cartridge Hand-piece (MFR-H4-
	DS) and Workstand (MFR-WSPT)
MFR-UK5	Desolder Hand-piece (MFR-H5-DS) and
	Workstand (MFR-WSDSX)
MFR-UK6	Solder Cartridge Hand-piece (MFR-H6-
	SSC) and Workstand (MFR-WS2)
MFR-H5-DS-C	Desolder Hand-piece (MFR-H5-DS) and
	Workstand cradle (MFR-WSDSCB)

Lead-Free Process Identification		
WS1G	12	Green Universal Auto Sleep
		Workstand
WS2G		Green Solder Workstand (PS-900)
WS1CG		Green Solder Rework Cradle
		Replacement for WS1 Workstand
WS2CG		Green Solder Rework Cradle
		Replacement for WS2 Workstand
AC-CK1	13	Green Identification Ring for OKi
		Cartridges (Pack of 50)
AC-CK3		Green Identification Ring for SSC
		Cartridges (Pack of 50)
AC-CK4	14	Green Identification Ring for OKi
		Tips (Pack of 50)

Miscellaneous Accessories	
AC-BRUSH-P 15	Soft Brass Brush (Pack of 6)
AC-CP2	Cartridge and Tip Removal Pad
AC-FX1 16	Fume Extraction Kit
AC-IK	Interlocking / Mounting Kit
MFR-PM70	Power Meter for MFR Series
PS-PM900	Power Meter for PS-900
AC-Y10	Yellow Sponge for WS1 Workstand
	(Pack of 10)
AC-YS4	Yellow Sponge Round for WS2
	Workstand (Pack of 10)
AC-BP	Brass Pad (Pack of 10)

Desoldering Ac	ccessories
MFR-DC10 17	Disposable Collection Chamber for
	MFR-H5-DS (pack of 10)
MFR-DC100	Disposable Collection Chamber for
	MFR-H5-DS (pack of 100)
MFR-HDCA 1	8 Coil Assembly for MFR Desolder
	Hand-piece
MFR-PG	Replacement Pistol grip for MFR-
	H5-DS Hand-piece
AC-SK1	Seal Kit Collection Chamber
	(pack of 2)
AC-VP	Vacuum Port
AC-VL	ESD Air Hose
AC-VPF	Vacuum Port Filter (pack of 5)
LM-PS	Power supply for MFR-WSDSX
	with multi plug adapters
AC-TC	Desoldering Tip Cleaner











PS-900 Production Soldering



The PS-900 provides power and exceptional thermal control in a small benchtop footprint.

Key Features & Benefits

- ▶ SmartHeat® temperature control
- ▶ Ergonomic, lightweight handle
- Rugged cast aluminum housing
- Added plating thickness to tips
- Low cost, quick-change heater coil





	Description
	Complete System
1	Power Supply
2	Hand-piece (PS-H3) and Coil Assembly (PS-CA3)
3	Workstand, Black
6	Economical and Affordable Chisel Solder Tip 1.5mm (.06")
sso	ries Available:
4	Hand-piece only, NO Coil Assembly
5	Coil Assembly for SxV Soldering Tips and CxV Blade Tips ONLY
	Auto-sleep Workstand, Black
	Auto-sleep Workstand, Green
	Tip Removal Pad
	2 3 6 850 4







ONLY AVAILABLE ON PS-900 SYSTEM AND FOR USE WITH PHT TIPS

PS-CA1	7	Coil Assembly for PHT Soldering Tips ONLY
PS-HC1		Hand-piece (PS-H3) and Coil Assembly (PS-CA1)
PS-H3	8	Hand-piece only, NO Coil Assembly



PHT Light Load, Fine Access Soldering Tips



PS-900 Production Soldering

Technical Specifications

Power Supply

Ambient Operating Temperature	10 - 40°C
Maximum Enclosure Temperature	65°C
Input Line Voltage	100 - 240 VAC
Input Line Frequency	50/60 Hz
Power Consumption	90 Watts max.
Output Power	60 Watts max. at 22°C ambient temperature
Output Frequency	450 KHz
Power Cord (3-wire)	183 cm 18/3 SJT
Dimensions W x D x H	80 x 160 x 115 mm (3.1" x 6.3" x 4.5")

Sol	ldering	Handle	and	Coil	Assemb	oly
Tin	to Cro	und Dat	ontial			_

Soldering nandle and Coll Assemb								
Tip-to-Ground Potential	< 2 mV							
Tip-to-Ground Resistance	< 2 ohms							
Idle Temperature Repeatability	± 1.1°C in still air							
Handle Cord Assembly Length	122 cm – burn proof, ESD safe							
Connector	3-pin power connector							
Overall length (with tip)	230 mm (9.06") with standard tips							
Grip diameter	13 mm (0.51")							
Tip to grip	58 mm (2.28")							
Tip shaft diameter	8.0 mm (0.31")							
Tip length	82 mm (3.23") to 93 mm (3.66") (typical)							
Workstand W x D x H	105 x 175 x 90 mm (4.1" x 6.9" x 3.5")							



Tip Soldering Hand-Piece with PS-CA3 Coil Assembly


PS-900-Solar



Key Features & Benefits

- Superior photo voltaic tabbing and buss soldering
- Lower thermal stress on solar cells
- ▶ Reduces the likelihood of micro-cracking
- Produces a controlled, high quality solder joint
- Calibration-free system
- Specially designed STV-DRH440A hoof tip for high performance









Part No.	Includes
PS-900-Solar	PS-PW900 Power Supply, PS-900-PC9 Hand-piece
	with long cord (274cm / 9ft) & PS-CA3 Coil Assembly,
	STV-DRH440A soldering tip, WS2-NS Workstand,
	AC-CP2 tip removal pad

STTC Soldering Cartridges

STTC SOLDERING CARTRIDGES	Compatible with: MX-500, MX-	5000	and MX-5200 Systems / MX-RM3E	and MX-H1-AV hand-pieces
0.04" 1.0mm	STTC-125P STTC-825P	CHISEL	0.10" — 6.0mm 0.24"	STTC-136P STTC- 8 36P
0.04" - 36" - 9.1mm	STTC- 5 25 STTC- 0 25 STTC- 1 25 STTC- 8 25		.10" 9.9mm	STTC- 5 36 STTC- 0 36 STTC- 1 36 STTC- 8 36
0.055° 0.24° 6.0mm 1.4mm	STTC-138P STTC- 8 38P		.12" 4.8mm	STTC-513 STTC-013 STTC-113 STTC-813
9.9mm 11.5mm	STTC- 5 38 STTC- 0 38 STTC- 1 38 STTC- 8 38		.85° 21.6mm	STTC-020 STTC-120 STTC-820
1.5mm	STTC- 5 99 STTC- 0 99 STTC- 1 99 STTC- 8 99		7.6mm 7.6mm	STTC-517 STTC-017 STTC-117 STTC-817
0.07° 1.8mm	STTC-137P STTC-837P		11.4mm 1.4mm 5.0mm	STTC- 5 65 STTC- 0 65 STTC- 1 65 STTC- 8 65
1.78mm	STTC- 5 37 STTC- 0 37 STTC- 1 37 STTC- 8 37	ONICAL	.25mm .52" .13.2mm	STTC-590 STTC-090 STTC-190 STTC-890
.07' ₁ 1 1.78mm 39" →-9.9mm →	STTC- 5 98 STTC- 0 98 STTC- 1 98 STTC- 8 98	ŏ	0.4mm 31" +7.9mm +	STTC-526 STTC-026 STTC-126 STTC-826
.63" 16.0mm	STTC- 5 42 STTC- 0 42 STTC- 1 42 STTC- 8 42		016" 8.4mm	STTC-522 STTC-022 STTC-122 STTC-822
4.7mm 1.08" 1.08" 1.03mm	STTC- 5 14 STTC- 0 14 STTC- 1 14		0.016" 8.5mm 1	STTC-145P STTC- 8 45P

STTC Soldering Cartridges

STTC SOLDERING CARTRIDGES	Compatible with: MX-500, MX-5	000 a	nd MX-5200 Systems / MX-RM3E a	nd MX-H1-AV hand-pieces
.54" 13.7mm	STTC- 5 06 STTC- 0 06 STTC- 1 06 STTC- 8 06 STTC- 5 45	CONICAL	.66" 16.7mm	STTC- 5 07 STTC- 0 07 STTC- 1 07
.016" 	STTC-545 STTC-045 STTC-145 STTC-845 STTC-540		1.3mm .86" .21.8mm	STTC- 5 41 STTC- 0 41 STTC- 1 41 STTC- 8 41
0.4mm	STTC- 0 40 STTC- 1 40 STTC- 8 40	BEVEL	30° 30° 14 20m	STTC- 5 46 STTC- 0 46 STTC- 1 46 STTC- 8 46
.02" -18" -18" -18" -18" -18" -18" -18"	STTC-011 STTC-111		0.25° 6.4mm	STTC-147P STTC- 8 47P
.19" +- .02" 4.8mm +- .0.5mm	STTC- 5 16 STTC- 0 16 STTC- 1 16 STTC- 8 16		0.07° 1.78mm	STTC- 5 47P
0.5mm .57" .14.5mm	STTC-544 STTC-044 STTC-144		1.78mm -9.9mm	STTC- 0 35 STTC- 1 35
.02" 15.2mm t 0.5mm	STTC-844 STTC-543 STTC-043 STTC-143		.07" 11.7mm 1.78mm 30°	STTC- 5 05 STTC- 0 05 STTC-105
0.04° 1.0mm = 0.25°	STTC-843 STTC-101P STTC-801P		1.78mm 5.56" 14.2mm	STTC- 5 47 STTC- 0 47 STTC- 1 47 STTC- 8 47
.04" 9.9mm 1.0mm	STTC- 5 31 STTC- 0 31 STTC- 1 31			
.53* 13.5mm 1 1.0mm	STTC- 5 01 STTC- 0 01 STTC- 1 01			

00 8	iliu wx-5200 Systems / wx-nwsc a	nd WA-ITI-AV nand-pieces
CONICAL	.66° 16.7mm	STTC- 5 07 STTC- 0 07 STTC- 1 07
	1.3mm	STTC-541 STTC-041 STTC-141 STTC-841
BEVEL	00 50 50 50 14.2mm	STTC- 5 46 STTC- 0 46 STTC- 1 46 STTC- 8 46
	0.25 [†] 6.4mm 0.07 [†] 1.78mm	STTC-147P STTC- 8 47P
	1.78mm 39"	STTC- 5 35 STTC- 0 35 STTC- 1 35
	.07" 11.7mm 1.78mm 30°	STTC- 5 05 STTC- 0 05 STTC- 1 05
	1.78mm 14.2mm	STTC- 5 47 STTC- 0 47 STTC-147 STTC- 8 47
	1.78mm 30° 1.78mm 30° 1.78mm 30°	STTC-035 STTC-135 STTC-505 STTC-005 STTC-105 STTC-547 STTC-047 STTC-147

UFTC UltraFine Soldering Cartridges

	UFTC ULTRAFINE SOLDERING CARTRIDGES	Compatible with: MX-5000 and N	ЛХ-52	200 Systems and MX-H2-UF hand-ր	iece
CONICAL	0.005 <u>*</u> 0.13mm	UFTC-7CN01	CHISEL	0.02" 5.1mm 0.6mm	UFTC-7CH06
	0.2'— 5.1mm 0.2mm	UFTC-7CN02		0.024*	UFTC-7CHL06
	0.008 0.2mm	UFTC-7CNB02		0.03°	UFTC-7CH08
	0.02° 5.1mm 0.02° 0.4mm	UFTC-7CN04		0.35' 8.97mm 0.031' 0.8mm	UFTC-7CHL08
	0.02" - 0.31' - 8,0mm	UFTC-7CNL04		0.05' 5.1mm 0.05'	UFTC-7CH12
	0.22° 5.5mm 0.016° 0.4mm	UFTC-7CNB04			
HOOF	0.031'45'	UFTC-7DRH408			
	0.048'45' 1.21mm	UFTC-7DRH412			

7 = 700 Series for most standard applications


SMTC Rework Cartridges

	SMTC REWORK CA	AITTIIDGES	All u	IIIIeiisioi	is snowi	n are in mm (inc	hes)							
			Α	D	В	SMT TYPE				Α	A2	D	В	SMT
S C O	A	SMTC-505 SMTC-005 SMTC-105	1.7 (.068)	1.27 (.05)	2.5 (.10)	SOT-32	TUNNEL	A A2	SMTC-004 SMTC-104		5.08 (.20)	2.3 (.90)	4.32 (.17)	sc
		SMTC-596 SMTC-096 SMTC-196	1.78 (.070)	1.02 (.040)	1.02 (.040)	Chip 0402, 0603		<u> </u>	SMTC-006 SMTC-106	5.08 (.20)	5.08 (.20)	2.3 (.90)	10.16 (.40)	SOI
		SMTC-588 SMTC-088 SMTC-188	2.03 (.080)	1.52 (.60)	1.27 (.050)	Chip 0402, 0603,			SMTC-0142 SMTC-1142					SO
	В	SIVITC-188	, ,		,	0805		В	SMTC-047 SMTC-147		8.51 (335)		1	DI
		SMTC-501 SMTC-001 SMTC-101	2.3 (.090)	1.8 (.070)	1.3 (.050)	Chip 0805			SMTC-126	8.64	8.0	1.88	,	SO
		SMTC-502 SMTC-002 SMTC-102	3.6 (.14)	1.8 (.07)	1.5 (.06)	Chip 1206,1210			SMTC-007 SMTC-107	9.53	9.53	3.20	18.3	so
	SMTC-132	3.81 (.150)	2.54 (.10)	2.41 (.095)	Chip Box B EIA SOPM-3528			SMTC-009 SMTC-109		9.53 (.375)		15.75 (.620)	S()	
		SMTC-536 SMTC-036 SMTC-136	4.8 (.190)	4.06 (.16)	2.8 (.110)	Chip Box B EIA SOPM-4532			SMTC-010 SMTC-110					
		SMTC-503 SMTC-003 SMTC-103	4.83 (.190)	1.91 (.075)	2.03 (.080)	Chip 1812			SMTC-040 SMTC-140					SO SO

		Α	A2	D	В	SMT TYPE
→ D ←	SMTC-004 SMTC-104			2.3 (.90)	4.32 (.17)	SOIC-8
A A2	SMTC-006 SMTC-106				10.16 (.40)	SOIC-14, 16
	SMTC-0142 SMTC-1142				8.89 (.350)	SOIC-14
B B	SMTC-047 SMTC-147				6.35 (.250)	DPAC
	SMTC-126	8.64 (.340)		1.88 (.074)	18.8 (.740)	SOJ-28, SOM-32
	SMTC-007 SMTC-107				18.3 (.720)	SOIC-28
	SMTC-009 SMTC-109					SOIC-24
	SMTC-010 SMTC-110	9.53 (.375)	9.53 (.375)	3.20 (.125)	13.20 (.520)	SOIC-20
	SMTC-040 SMTC-140				25.9 (1.02)	SOJ-40, SOM-32

5 = 500 Series & 0 = 600 Series for temperature sensitive applications. 1 = 700 Series for most standard applications. 8 = 800 Series for Ceramic and high thermal demand applications.

SMTC Rework Cartridges



PTTC Tweezer Cartridges TATC Talon Cartridges

	PTTC TWEEZER CARTRIDGES	Compatible with: MX-5000 and MX-5200 Systems and MX-PTZ Precision Tweezers hand-piece
CONICAL	0.90" 23mm 0.4mm	PTTC-601 PTTC-701 PTTC-801
	0.016° 0.4mm	PTTC-701B PTTC-801B
BLAUE	0.05' 16.5mm 0.05' 1.3mm	PTTC-602 PTTC-702 PTTC-802
	0.65' 16.5mm 2.0mm	PTTC- 6 03 PTTC- 7 03 PTTC- 8 03
	0.14* 0.48* 12.1mm 3.5mm	PTTC-608B PTTC-708B PTTC-808B
	0.25° 0.25° 0.7mm 0.25° 0.25° 0.7mm	PTTC-604 PTTC-704 PTTC-804
	0.28*	PTTC- 6 05 PTTC- 7 05 PTTC- 8 05
	0.28*22°20.5mm	PTTC- 6 06 PTTC- 7 06 PTTC- 8 06
	0.28*	PTTC- 6 07 PTTC- 7 07 PTTC- 8 07

TATC TALON CARTRIDGES	Compatible with: MX-500 Systems and MX-Talon hand-piece
0.5mm 0.35mm	TATC-609
1.245mm 0.2° 0.5mm 0.47° 1.2mm	TATC-601
.05" 1.27mm	TATC-608
.10° 2.54mm 40° 10.16mm .25° 6.35mm	TATC-602
0.75mm	TATC- 6 05
05" 1.27mm 15.75mm	TATC-603
05" 1.27mm 20.57mm 33" 20.57mm	TATC-604
03° 1.1° 27.94mm	TATC- 6 06

STDC Desolder Cartridges

Compatible with: MX-500 MX-5000 and MX-5200 Systems, MX-DS1 Desoldering hand-piece All dimensions shown are in mm (inches)

STDC	D ESOLDER	CARTRIDGES
-------------	------------------	------------







Long Reach

	Α	В	С	TYPE
STDC-102	0.64	1.40	11.43	Standard
STDC-802	(.025)	(.055)	(.45)	
STDC-103	0.76	1.68	11.17	Standard
STDC-803	(.029)	(.066)	(.44)	
STDC-104	1.02	1.78	10.92	Standard
STDC-804	(.04)	(.07)	(.43)	
STDC-105	1.27	2.03	10.66	Standard
STDC-805	(.05)	(.08)	(.42)	
STDC-106	1.52	2.29	10.41	Standard
STDC-806	(.06)	(.09)	(.41)	
STDC-107	2.41	3.18	9.14	Standard
STDC-807	(.09)	(.12)	(.36)	
STDC-703L	0.76	1.68	21.33	Long
STDC-803L	(.03)	(.06)	(.84)	Reach
STDC-704L	1.02	1.79	21.08	Long
STDC-804L	(.04)	(.07)	(.83)	Reach
STDC-705L	1.27	2.03	20.82	Long
STDC-805L	(.05)	(.08)	(.82)	Reach

SSC Soldering Cartridges


			o del	Compatible with: MFR-1160 S	ystem and MFR-H6-SSC Hand-piece
	SSC SOLDERING CARTRIDGES				
CHISEL	04" 9.1mm	SSC- 6 71A SSC- 7 71A	ONICAL	.01" .52" .25mm .13.2mm	SSC- 6 90A SSC- 7 90A
O	.04" 11mm	SSC-625A SSC-725A	00	.016° .75°	SSC-645A SSC-745A
	.06° 10mm	SSC-638A SSC-738A		02" 11.4mm	SSC-622A SSC-722A
	1.78mm	SSC- 6 37A SSC- 7 37A		0.51mm .45" — 11.4mm	SSC- 6 26A SSC- 7 26A
	39° 9.9mm	SSC- 6 72A SSC- 7 72A		.73" -18.5mm	SSC- 6 54A SSC- 7 54A
	.63"	SSC-642A SSC-742A		15.2mm	SSC-601A SSC-701A
	1.78mm 65° 16.5mm	SSC-670A SSC-770A		055°	SSC- 6 74A SSC- 7 74A
	1 9.9mm 1 10° 2.9mm	SSC- 6 36A SSC- 7 36A	H00F	05" 17.8mm 11.27mm	SSC-639A SSC-739A
	3.3mm	SSC-613A SSC-713A		.016" 17.8mm	SSC-661A SSC-761A
	112" 3.0mm 65" 16.5mm	SSC- 6 46A SSC- 7 46A	KNIFE	18" 455 45 16.25mm 16.25mm	SSC-673A SSC-773A
	5.3mm 1 10mm	SSC- 6 17A SSC- 7 17A		4.5mm 45° 45° 16.25mm 16.25mm 0.5mm	SSC-647A SSC-747A
BEVEL	1.78mm - 14.2mm - 14.2mm	SSC- 6 67A SSC- 7 67A			

SxV Soldering Tips

Compatible with: PS-900, MFR-1120, MFR-2220, MFR-2222 Systems. PS-HC3 and MFR-H2-ST hand-pieces. PS-CA3 and MFR-CA2 Coil Assemblies SXV SOLDERING TIPS NEW SFV-CH25 SFV-CH10A __0.43"__ 11.0mm 0.719" 18.3mm STV-CH25 ш STV-CH10A 0.04" . 0.1 SCV-CH25 SCV-CH10A SFV-CH30AR SFV-CH10AR 13.7mm STV-CH10AR STV-CH30AR 3.0mm 1.0mm 65' SCV-CH10AR SCV-CH30AR 16.5mm NEW SFV-CH10 SFV-CH50A __0.43<u>"__</u> 11.0mm 0.44"__ 11.3mm STV-CH10 STV-CH50A 0.04" 5 0mm SCV-CH10 SCV-CH50A NEW SFV-CH15A SFV-CH50AR 461" 0.44" 11.7mm STV-CH15A STV-CH50AR 197" SCV-CH15A SCV-CH50AR SFV-CH15AR SFV-CH50 __.528"_ 13.4mm 0.4"_ 10.0mm STV-CH15AR STV-CH50 0.2" 1.5m 5.0mn SCV-CH15AR **SCV-CH50** SFV-CHB15 SFV-CNL03AR 0.06" 724" CAL STV-CHB15 18.4mm STV-CNL03AR .01" _0.48" 0.3mm SCV-CHB15 SCV-CNL03AR 12.2mm NEW SFV-CH18AR 0.016" SFV-CNB04A 0.61" .528"__ 13.4mm 15.5mm STV-CH18AR STV-CNB04A 1.8mm SCV-CH18AR SCV-CNB04A 0.21" 5.4mm NEW SFV-CH20 SFV-CN05A __0.43<u>"__</u> 11.0mm 0.72" 18.2mm STV-CH20 STV-CN05A 0.08" 0.016"__ SCV-CH20 SCV-CN05A 0.4mm NEW SFV-CH24A SFV-CNB04AR €016 .719" 18.3mm STV-CH24A STV-CNB04AR 0.094 _19.6mm .77" SCV-CH24A SCV-CNB04AR SFV-CH25AR SFV-CNL04 __.528"__ 13.4mm 0.53"_ .10" 13.6mm STV-CH25AR STV-CNL04 0.016"___< 2.5mm SCV-CNL04 SCV-CH25AR

F = FR4 / Fiber Glass, for most standard applications **T** = Temperature Sensitive **C** = Ceramic for high thermal demand applications.

SxV Soldering Tips CxV Blade Tips




,		
2.0mm 2.08" -	20.7mm .81*	S F V-DRH420AR S T V-DRH420AR S C V-DRH420AR
0.10° 2.5mm	45° 0.51° 13.0mm	S F V-DRH20CP S T V-DRH20CP S C V-DRH20CP
3.0mm	45° 20.4mm 0.8° ×	S F V-DRH430AR S T V-DRH430AR S C V-DRH430AR
.120 1.00m	fr Ubos	S F V-DRH630AR S T V-DRH630AR S C V-DRH630AR
0.137° 3.47mm	0.48° 12.2mm 10.079° 2mm	S F V-DRH420A S T V-DRH420A S C V-DRH420A
0.14* 3.6mm	45° 0.51° 13.0mm	S F V-DRH30CP S T V-DRH30CP S C V-DRH30CP
	20th State of the	S F V-DRH440R S T V-DRH440R S C V-DRH440R
155° 4.62mm	ATV (7 distant	S F V-DRH640AR S T V-DRH640AR S C V-DRH640AR
0.18° 4.6mm	45° - 0.51' - 13.0mm	S F V-DRH40CP S T V-DRH40CP S C V-DRH40CP
	0.52° NEW	S F V-DRH440A S T V-DRH440A S C V-DRH440A
.12° → 3.0mm <u>u</u>	18.7mm	S F V-DRK30AR S T V-DRK30AR S C V-DRK30AR
1.8mm .07* 4.5mm .18* _	, 4	S F V-DRK45AR S T V-DRK45AR S C V-DRK45AR

CxV BLADE	TIPS		Α
0.02" N E W	CFV-BL100	CCV-BL1	00 10mm (.40")
0.02 0.5mm 0.36" 9.1mm	C F V-BL25	60 C C V-BL25	0 25mm (1")
<u> </u>	CFV-BL35	60 C C V-BL35	0 35mm (1.4")
A	C F V-BL40	00 C C V-BL40	0 40mm (1.6")
	C F V-BL50	00 C C V-BL50	0 50mm (2")

F = FR4 / Fiber Glass, for most standard applications **T** = Temperature Sensitive **C** = Ceramic for high thermal demand applications.

PHT Soldering Tips



SxP Soldering & Rework Cartridges

SxP Soldering & Rework Cartridges	Compatible with: MFR-1110, MFR	-1161	, MFR-1351, MFR-2211, MFR-2241	Systems and MFR-H1-SC hand-piece
SFP-CH10 STP-CH10	IICAL	0.016° 8.6mm 0.4mm	S F P-CN04 S T P-CN04 S C P-CN04	
1mm	S C P-CH10 S F P-CH15	CONI	0.016 0.4mm 0.4mm	S F P-CNB04 S T P-CNB04 S C P-CNB04
0.39° 10mm 1.5mm	S T P-CH15 S C P-CH15		0.59° 	SFP-CNL04 STP-CNL04 SCP-CNL04
0.474* 12.04mm 1.5mm	SFP-CHB15 STP-CHB15		0.02* 4.95mm 0.5mm	S F P-CN05 S T P-CN05 S C P-CN05
0.4*	S C P-CHB15 S F P-CH20		0.02° 14.7mm 0.05mm	S F P-CNB05 S T P-CNB05 S C P-CNB05
0.08° 1 10.0mm 2.0mm 1	0.08*+ STP-CH20		0.02' 13.0mm	S F P-CNL06 S C P-CNL06
0.08* 2.0mm	SFP-CHL20 STP-CHL20	BEVEL	0.56° 14.22mm 1.0mm	S F P-BLV10 S T P-BLV10 S C P-BLV10
	S C P-CHL20 S F P-CH25	OOF	0.6" 0.02 0.5mm	S F P-DRH05 S T P-DRH05 S C P-DRH05
0.1° 2.5mm	S T P-CH25 S C P-CH25	Ĭ	0.039" ————————————————————————————————————	S F P-DRH610 S T P-DRH610 S C P-DRH610
0.12° 0.43° 11.0mm	S F P-CH30 S T P-CH30 S C P-CH30		1.5mm 30° 0.06" 16.5mm 0.65"	S F P-DRH15 S T P-DRH15 S C P-DRH15
0.14* 3.5mm	S F P-CH35 S T P-CH35		1.5mm	S F P-DRH615 S T P-DRH615 S C P-DRH615
0.43° 11.0mm	S C P-CH35		0.14* 3.5mm 70* 17.78mm	S F P-DRH35 S T P-DRH35 S C P-DRH35
0.3° - 7.6mm 0.2° 5mm	S F P-CH50 S T P-CH50 S C P-CH50	KNIFE	0.2" 5.0mm 0.63" 18mm -	S F P-DRK50 S T P-DRK50 S C P-DRK50

F = FR4 / Fiber Glass, for most standard applications T = Temperature Sensitive C = Ceramic for high thermal demand applications.

RxP Rework Cartridges

Compatible with: MFR-1110, MFR-1161, MFR-1351, MFR-2211, MFR-2241 Systems and MFR-H1-SC hand-piece. All dimensions shown are in mm (inches) RXP REWORK CARTRIDGES Α R D **SMT TYPE** .36" 9.14mm RFP-BL1 10 .02" -BLAD RCP-BL1 0.5mm (0.41)RFP-BL2 15.6 RCP-BL2 (0.62)RFP-BL3 22.1 RCP-BL3 (0.87)RFP-DL1 5.18 3.22 Tunnel 10.16 LONNE RCP-DL1 (0.204)(0.40)(0.127)SOIC-14-16 RFP-DL2 5.18 4.32 2.29 Tunnel RCP-DL2 (0.204)SOIC-8 (0.17)(.09)RFP-DL3 Tunnel 6.86 11.15 2.29 RCP-DL3 SOIC-16 (.270)(0.44)(.09)RFP-SL1 2.34 0805 Chip 1.37 1.78 RCP-SL1 (.092)(.054)(.07)Package SLOT RFP-SL2 3.48 1.63 1.78 1206 Chip RCP-SL2 (.137)(.064)Package (.07)Α **A2** D В B2 **SMT TYPE** 12.70 11.43 3.81 15.24 13.97 RFP-QD4 PLCC 32 RCP-QD4 (.500)(.450)(.150)(.600)(.550)RFP-QD6 17.78 16.76 3.81 17.78 16.76 PLCC 44 RCP-QD6 **A2** (.700)(.660)(.150)(.700)(.660)RFP-QD7 25.27 24.38 5.59 25.27 24.38 PLCC 68 RCP-QD7 (.995)(.960)(.220)(.960)(.995)20.32 19.30 20.32 RFP-QD10 3.81 19.30 PLCC 52 RCP-QD10 (.800)(.760)(.150)(.800)(.760)В RFP-QD15 13.34 12.32 2.79 13.34 12.32 TQFP 80 **B2** RCP-QD15 (.525)(.485)(.110)(.525)(.485)16.13 16.13 3.30 16.13 RFP-QD19 16.13 QFP 44 RCP-QD19 (.635)(.635)(.130)(.635)(.635)22.48 22.48 RFP-QD20 16.51 16.51 3.30 **QFP 100** RCP-QD20 (.650)(.650)(.130)(.885)(.885)

F = FR4 / Fiber Glass, for most standard applications **T** = Temperature Sensitive **C** = Ceramic for high thermal demand applications.

TxP Tweezer Cartridges DxP Desoldering Tips

	TxP Tweezer Cartridges	Compatible with: MFR-1140, MFR-2240, MFF	R2241 Systems and MFR-H4-TW hand-piece
ADE	0.03' 14mm 1.0mm	T F P-BLP1 T T P-BLP1 T C P-BLP1	1.0mm x 14mm (.04" x .55")
BLA	0.75° 1.55°	T F P-BLP2 T T P-BLP2 T C P-BLP2	2.0mm x 14mm (.08" x .55")
	.015" 19.1mm .38mm	T F P-CNP1 T T P-CNP1 T C P-CNP1	Conical 0.4mm x 19.1mm (.015" x .75")
\	0.028° 0.57mm 0.055° 1.4mm		Α
HEAVY DUT		T F P-BLH40 T T P-BLH40 T C P-BLH40	6.35mm (.25")
		T F P-BLH50 T T P-BLH50 T C P-BLH50	16mm (.62")
		T F P-BLH60 T T P-BLH60 T C P-BLH60	20.5mm (.81")
		T F P-BLH70 T T P-BLH70 T C P-BLH70	28mm (1.1")

Compatible with: MFR-1150, MFR-1350, MFR-1351 systems with MFR-H5-DS hand-piece and previous MFR-DSX, -DSI, -SDX, -SDI Systems with MFR-HDS hand-piece.

DxP Desoldering Tips	All dimensions shown are in	n mm (inches)		·
		Α	В	TYPE
	D F P-CN2	0.64	1.78	Standard
B	D C P-CN2	(.025)	(.070)	Stanuaru
	D F P-CN3	0.76	2.03	Standard
A	D C P-CN3	(.030)	(.080)	Stanuaru
	D F P-CN4	1.02	2.28	Ctandard
	D C P-CN4	(.040)	(.090)	Standard
	D F P-CN5	1.27	2.64	Standard
5.54mm	D C P-CN5	(.050)	(.104)	Standard
0.218"	D F P-CN6	1.52	2.84	Standard
Standard	D C P-CN6	(.060)	(.112)	Staridard
	D F P-CN7	2.41	3.63	Standard
	D C P-CN7	(.095)	(.143)	Glaridard
	D F P-CNL3	0.76	2.03	Long Reach
	D C P-CNL3	(.030)	(.080)	Long neach
12.80mm 0.503"	D F P-CNL4	1.02	2.28	Laura Darah
Long Reach	D C P-CNL4	(.040)	(.090)	Long Reach
	D F P-CNL5	1.27	2.64	Lawa Danah
	D C P-CNL5	(.050)	(.104)	Long Reach

Convection Rework Overview

SYSTEMS SERIES

MANUAL AND MODULAR SYSTEMS



MRS-1100A Modular Rework System



APR Scorpion Rework Systems

FOR SMALL TO MEDIUM

HANDHELD SERIES

PRE-HEATERS



PCT-1000 Programmable Pre-Heater



PCT-100 Pre-Heater

DIGITAL

ANALOG

Convection Rework Overview

SEMI-AUTOMATED SYSTEMS



APR-5000-DZ Rework Systems

B O A R D S



APR-5000-XLS Rework Systems

FOR LARGE BOARDS

CONVECTION TOOLS



HCT-1000 Programmable Convection Tool



HCT-900 Convection Tool

DIGITAL

ANALOG

Scorpion Rework System

The Scorpion Advanced Package Rework System ensures both accurate component placement and custom tailored reflow profiles in one user friendly, single platform rework system.

The challenges of array package rework, and the inability to easily inspect placement accuracy, call for a solution that allows for simultaneous viewing of Printed Circuit Board pads and component balls for accurate placement.

The Scorpion Rework System fills this need with quick, accurate placement through the use of an all new vision system employing dual image overlay technology. This new vision system features LED lighting both top and bottom for shadow-free component visualization and component alignment. The HD camera is ready to go out of the box.

The two-head design allows the Scorpion Rework System to be tailored to the users specific rework needs and allows precision alignment of the smallest BGAs, QFNs and Micro SMDs with the highest accuracy. The open-ended board holder fits a wide vari-ety of large, small and odd-shaped boards while allowing precise positioning over the patented dual subzone preheater.

The standard auto-profile mode ensures fast and easy profile creation with a minimum of setup time. By selecting your tempera-ture targets any operator can quickly and accurately create reflow profiles for a wide variety of boards, and then save them in memory for future use.

Source temperatures and time intervals can be modified "On-the-Fly", eliminating the need to wait for the current profile to terminate before modifications can be made. Precise solder joint temperatures are measured and displayed on a real time graphical display, thus providing the necessary data to accurately and easily establish the optimum reflow profile for each particular application within minutes.

Systems

APR-1100-SRS Scorpion Rework System with SmartPlace Technology



APR-1200-SRS Scorpion Rework System, SmartPlace Technology & Precision Placement Package



Upgrade Kits

APR-SRS-UK1 Precision Placement Package

APR-SRS-UK2 Contactless IR Sensor

APR-SRS-UK3 Side-view Camera

(see details on page 34)



Scorpion Rework System

Hardware Features

- Desktop sized
- 2800W dual zone preheater with 550W top heater
- Single phase 208-240VAC, 50/60Hz, 13A
- Design allows customers to customize the unit to meet their needs
- A 343mm (13.5") x open-ended PCB holder with micrometer adjustment
- Mechanical X and Z axis movement on linear bearings for long-life and minimal maintenance
- Component is retracted automatically at the end of reflow when removing parts
- Linux-based integral computer
- External USB for file transfer
- High definition SmartPlace vision system which uses dual CMOS sensors to assist in the placement of components and requires no calibration
- Optional Precision Placement Head for ultra fine pitch components with placement accuracy of .0254mm (.001") (APR-SRS-UK1)
- Contactless IR sensor for auto start at pre-determined temperatures (APR-SRS-UK2)
- New side-view camera for increased reflow visibility (APR-SRS-UK3)

Software Features

- Auto-Profiling
- On the fly profile management of target set points, adding and subtracting time zones, and profile measurement points
- Real time graphical display of solder joint temperatures
- Internal storage of profile data with expansion and transfer via a USB flash drive
- Graphics-based user interface for simple operation
- Simple heater calibration
- Password protection for operators and engineers

Smartplace Technology Vision System Features

- Dual, full color HD camera
- Synchronized 50x Zoom
- 45mm x 45mm (1.77" x 1.77") viewing area
- Selectable camera transition
- Diffused LED lighting for shadow-free component alignment

Operations Features

- Uses existing APR-5000 Series reflow and vacuum nozzles
- Precision Placement head uses pick and place machine nozzles
- Small footprint, 457mm x 559 mm x 660mm (18"x 22" x 26")
- Made in the USA










Scorpion Rework System

Upgrade Kits

APR-SRS-UK1 Precision Placement Head

For placement accuracy to 0.0015" (.038mm)

Also included with kit: **Under Board Support UBS-SRS** PNZ-07 Vacuum Pick-Up Nozzle, 0.7mm O/D PNZ-24 Vacuum Pick-Up Nozzle, 2.4mm O/D PNZ-80 Vacuum Pick-Up Nozzle, 8.0mm O/D PNZ-AD Nozzle Adaptor for Fine Placer Head



Technical Specifications

Input Voltage	208-240VAC, 50/60Hz, 13 Amp Single Phase

Power Consumption

System Total 2800W

Pre-Heater		
Inner Zone*	900W	
Outer Zone*	1800W	
Reflow Heater	550W	

^{*} both heaters can be used at the same time

Temperature Control Type

Closed-Loop Control (Thermocouple)

Maximum Source Temperature

Reflow Head	400°C (752°F)
Pre-Heater (Inner/Outer)	350°C (662°F)
Airflow Control	Pre-Set to 8, 16 & 24/min
Supply	24V DC Blower
Operating Temperature	5°C (41°F) to 40°C (104°F)
Maximum Relative humidity	80% at 31°C (88°F) decreasing linearly to 50% at 40°C (104°F)
Maximum Altitude	2000m (6500 ft)
Pollution Degree	2 per IEC 644
Insulation category	II .

APR-SRS-UK2 Contactless IR Sensor

Features a remote temperature sensor to ensure repeatability



APR-SRS-UK3 Side-view Camera Facilitate visibility of reflow



Component Handling

Max. Size	45mm x 45mm
	(1.77" x 1.77")
Min. Size	0.51mm x 0.25mm
	(0.020" x 0.010")
Max. Weight	55 g (1.94 oz)

PCB Handling Capability

Max. Size	343mm (13.5") x open-ended
Max. Thickness	6mm (0.25")
Rework Area	305mm x 305mm (12" x 12")

Max. Field of View 45mm x 45mm (1.77" x 1.77")

System

- J - - - - - - - - - -	
Dimensions	457mm x 559mm x 660mm
WxDxH	(18" x 22" x 26")
Weight	63.5kg (140lbs)
System Warranty	One-year parts & labor
	90 days heaters & lamps
Approvals	TUV German standards, CE

Scorpion Rework System

Accessories

Included with APR-1100-SRS and APR-1200-SRS

FSL-SRS-3	Long spring PCB Finger 3mm (Pack 3)	
FSS-SRS-3	Short spring PCB Finger 3mm (Pack 3)	
AC-TC3	Thermocouple Multi-Colored Set, 36 Gauge (qty 2)	
VNZ-ORINGK	O-Ring Kit (assortment, qty 5 for each of the 4 sizes)	
SRS-VRT	Placement Verification Kit	
VNZ-12	Vacuum Pick-Up Nozzle,12mm, Reflow Head	
VNZ-08	Vacuum Pick-Up Nozzle, 8mm, Reflow Head	
VNZ-05	Vacuum Pick-Up Nozzle, 5mm, Reflow Head	
VNZ-01	Vacuum Pick-Up Nozzle, 1mm, Reflow Head	
AC-RP	Nozzle Removal Pad	
APR-VRT	Vacuum Nozzle Removal Tool	
20987	CSP Adjustable V Block	
19782	BGA Adjustable V Block	
KAP-100	Pre-cut Kapton Tape (qty 100)	
UBS-SRS	Under Board Support	



PNZ-07	Vacuum Pick-up Nozzle, 0.7mm O/D
PNZ-24	Vacuum Pick-up Nozzle, 2.4mm O/D
PNZ-80	Vacuum Pick-up Nozzle, 8.0mm O/D
PNZ-AD	Nozzle adapter for Precision Placement Head

Optional Accessories

FSL-6MM-SRS-3	Long PCB fingers, 6mm clip (pack of 3)
FSS-6MM-SRS-3	Short PCB fingers, 6mm clip (pack of 3)
SRS-AK	Accessories Kit
VAC-P100	Vacuum assist plate kit (pack of 100)
VNZ12-ORING	12mm O-Rings (pack of 50)
VNZ08-ORING	8mm O-Rings (pack of 50)
VNZ05-ORING	5mm O-Rings (pack of 50)
VNZ-005	Vacuum Pick-up Nozzle, 0.5mm O/D, 10mil hole
PF-1	Solder Paste/Flux Prep Plate
APR-OPTICAL-KIT	Optical Calibration Kit

Reflow Nozzles & other accessories - See page 39

The Scorpion system accepts the full range of APR and QX series reflow nozzles. Flux transfer plates and solder paste plates are available to ensure repeatable process control during the replacement operation.





VNZ Nozzles



CSP / BGA Adjustable V Block



Under Board Support



Accessories Kit



NZA Nozzles


APR-5000-DZ Advanced Package Rework System


The APR-5000-DZ Advanced Package Rework System provides closed-loop control, optimized vision and precise component placement on a compact platform of 19" x 30" (483mm x 762mm). Self contained pumps are standard on this compact platform allowing for easy benchtop setup.


Capable of handling boards up to 15" x 7.75" (381mm x 197mm) with standard fixtures (larger PCB Holder options exist if required) with a placement accuracy to 0.001" (0.025mm) and interconnection pitches as low as 0.012" (0.3mm), the APR-5000-DZ is ideal for reworking smaller assemblies such as cell phones and laptop computers.

The APR-5000-DZ System incorporates powerful, efficient and fast response convective top reflow heater and bottom dual zone pre-heaters for delivering fast ramp and tight delta temperature control horizontally, across the surface of PCBs up to 0.25" (6.35mm) thick, and vertically between the die and ball of the reworked components.

The single reflow/placement head can be moved to the correct position for rework allowing PCB assemblies with 2" (50mm) underside components to be stationary mounted above the pre-heater. An optional XY table (APR-TAB) can be added to minimize operator fatigue and is ideal for small PCB assemblies with less than .25" (6.4mm) underside components. In addition, the APR-5000-DZ-TAB is an APR-5000-DZ system with a pre-assembled XY table.







APR-5000-DZ System configurations and technical specifications on pages 40-41

APR-5000-XLS Advanced Package Rework System

The APR-5000-XLS Advanced Package Rework System provides board capability with small board precision. This system performs precise, cost effective rework of the widest range of PCBs and component types, from large boards up to 24.5" x 24.5" (622mm x 622mm) to components down to 0.020" x 0.010" (0.5mm x 0.25mm).

The flexible APR-5000-XLS System incorporates dual stage pre-heaters and has the thermal capacity and control to execute precise profiles of both large and small PCBs, delivering uniform temperature control horizontally, across the surface of PCBs up to 0.25" (6.35mm) thick, and vertically between the die and ball of the reworked component.

Motorized X,Y, Z adjustments speed placement and help ensure process repeatability. In addition, motorized Theta axis provides 360° rotation to simplify component orientation. Together, these advanced controls reduce operator fatigue, improve placement accuracy and provide process consistency.

Featured on the APR-5000-XLS Advanced Package Rework System is an innovative Split Vision System, which allows operators to view the opposite corners of a component, including splitting on rectangular components, with the necessary magnification to make its placement and registration fast and accurate.

Improved performance

New features:


- New dual simultaneously operating subzones provides additional power for faster and safer rework operations.
- New software enables fast and easy profiling
- New subzone design speeds up the process while allowing the operating temperatures to remain lower protecting the component and PCB


Key benefits:


- Increased Productivity
- Precise thermal control across critical assembly regions
- Reduction of rework cycle time protects the component under rework from thermal damage.
- Better management of the narrow lead-free process window without reaching excessive peak temperatures that damage components, connectors, other solder joints and the PCB substrate











APR-5000-XLS System configurations and technical specifications on pages 40-41

Accessories

Component Stenciling Templates

Metcal has designed a unique tool, Component Stenciling Templates, for printing on the underside of components. This easy procedure is designed for use on PBGA, CBGA, CSP balled devices as well as Land Grid Array (LGA) components. This is an ideal process for small components and situations where traditional stencil access is limited by the close proximity of adjacent components.

Dip Transfer

This process involves dipping a component into gel flux, depositing an exact amount of flux. This process is quick, consistent and clean, and negates the need to clean after reflow. Available for both solder balled and leaded devices. All kits are supplied with a metal spatula. Ideally select a dip plate that is half the diameter of the solder balls on components.

Tape Feeder

Picking up small surface mount components with tweezers is not practical and may damage the component. This is a unique way of presenting small components to a rework machine.


Demo PCB Kit

The board includes chip resistors, LLP, Micro SMD, QFP, PLCC, Fusion Packs, BGA and POP components to provide a versatile demonstration tool. It has also been pre drilled to allow for thermocouple attachment. Details of nozzles and rework process for the relevant component are printed on the back of the PCB.

Nozzles

A comprehensive range of standard reflow nozzles available to suit the most common array packages is available. The reflow nozzle works with vacuum pickup, the tweezer nozzle works with devices with limited area or multilayer structure by providing mechanical tweezer action pickup instead of vacuum pickup e.g. PoP, sockets, connectors, inductors, potentiometers and through-hole components.











Accessories & Nozzles

Part No.	DESCRIPTION	
BRP-KIT-LGA100-04	Full kit (3pcs) w/ base fixture, pattern & body plates for LGA100-0.4mm (also incl. clamp & squeegee)	
BRP-KIT-BASE	BRP kit base fixture only	
BRP-KP-LGA100-04	Kit plates (2pcs), pattern and body plates only (minus base) for LGA100-0.4mm	
BRP-KIT-FUSION-216	Full kit (3pcs) w/ base fixture, pattern & body plates for Fusion pack 216 (incl. clamp & squeegee)	
BST-256-100	Standard BST plate, clamp & squeegee, PBGA 256, 1.0mm pitch	
BST-256-127	Standard BST plate, clamp & squeegee, PBGA 256, 1.27mm pitch	
BST-388-127	Standard BST plate, clamp & squeegee, PBGA 388, 1.27mm pitch	
BRP-KP-FUSION-216	Kit plates pattern & body plates only (minus base) for Fusion pack 216	
TF-1T	Tape Feeder, Micro SMD with thumbwheel	
TF-2T	Tape Feeder, 0603 and 0402 with thumbwheel	
TF-3T	Tape Feeder, 0201 with thumbwheel	
NZA-490-490*	APR Reflow Nozzle 49mm x 49mm	
NZA-450-450	APR Reflow Nozzle 45mm x 45mm	
NZA-400-400*	APR Reflow Nozzle 40mm x 40mm	
NZA-350-350*	APR Reflow Nozzle 35mm x 35mm	
NZA-300-300	APR Reflow Nozzle 30mm x 30mm	
NZA-270-270	APR Reflow Nozzle 27mm x 27mm	
NZA-250-290	APR Reflow Nozzle 25mm x 29mm	
NZA-230-230*	APR Reflow Nozzle 23mm x 23mm	
NZA-280-150	APR Reflow Nozzle 28 mm x 15 mm	
NZA-200-200**	APR Reflow Nozzle 20 mm x 20 mm	
NZA-180-180***	APR Reflow Nozzle 18 mm x 18 mm	
NZA-150-150**	APR Reflow Nozzle 15 mm x 15 mm	
NZA-130-130***	APR Reflow Nozzle 13 mm x 13 mm	
NZA-100-100***	APR Reflow Nozzle 10 mm x 10 mm	
NZA-080-095***	APR Reflow Nozzle 8 mm x 9,5 mm	
NZA-080-080**	APR Reflow Nozzle 8 mm x 8 mm	
NZA-060-060***	APR Reflow Nozzle 6 mm x 6 mm	
NZA-030-ROUND	APR Reflow Nozzle 3mm ID round	
NZA-TW-180-180	APR Tweezer Nozzle 18mm x 18mm	
NZA-TW-150-150	APR Tweezer Nozzle 15 mm x 15 mm	
NZA-TW-130-130	APR Tweezer Nozzle 13 mm x 13 mm	
NZA-TW-100-100	APR Tweezer Nozzle 10 mm x 10 mm	
NZA-TW-080-080	APR Tweezer Nozzle 8 mm x 8 mm	
NZA-TW-060-060	APR Tweezer Nozzle 6 mm x 6 mm	
NZA-555-555-CGA	APR Reflow Nozzle 55.5mm x 55.5mm (column grid array nozzle)	
NZA-470-470-CGA	APR Reflow Nozzle 47mm x 47mm (column grid array nozzle)	
NZA-355-455-CGA	APR Reflow Nozzle 35.5mm x 45.5mm (column grid array nozzle)	
NZA-350-350-CGA	APR Reflow Nozzle 35mm x 35mm (column grid array nozzle)	
DTP-BGA	Set of 3 plates, apertures 28, 35 & 45mm, depth 0.012" (0.30mm) used for 1.27mm pitch	
	30 Mil BGA balls (.76mm)	
DTP-CSP	Set of 3 plates, apertures 10, 16 & 21mm, depth 0.006" (0.15mm) BGA/CSP used for BGAs with	
12 Mil balls (.3mm dia)		
DTP-40-8	8 Mil dip plate standard for 1mm pitch BGA with 20 Mil balls 0.02" (0.5mm)	
DTBK-USMD	Kit, uSMD Flux Transfer Blocks, set of 2 blocks, depth 0.003" (0.08mm) and 0.004" (0.10mm) used for	
solder balls 6-8 Mil (.15-2mm dia)		
DTBK-FC	Kit, Flip Chip Flux Transfer Blocks, set of 2 blocks, depth 0.001" (0.025mm) and 0.002" (0.051mm)	
APR-NK	APR-5000 Nozzle Kit (*Includes 1 of each)	
APR-NK-CSP	APR-5000 CSP and Micro SMD Nozzle Kit (**Includes 1 of each)	

(*** 1 included in both kits)







Part Numbers

Part No.	SYSTEMS DESCRIPTION	
APR-5000-DZ-ML	200-240 VAC Advanced Package Rework System	
APR-5000-DZ-TAB-ML	200-240 VAC Advanced Fackage Rework System with XY Table	
APR-5000-XLS-ML	200-240 VAC Advanced Package Rework System with Split Vision	
APR-5000-XL-ML	200-240 VAC Advanced Package Rework System 200-240 VAC Advanced Package Rework System	
Systems will be configured with de		
	00-DZ/-TAB, **APR-5000-XL / -XLS, ***APR-5000-DZ-TAB)	
VNZ-19	Vacuum Pick-Up Nozzle 19mm O/D**	
VNZ-12	Vacuum Pick-Up Nozzle 12mm O/D	
VNZ-08	Vacuum Pick-Up Nozzle 8mm O/D	
VNZ-05	Vacuum Pick-Up Nozzle 5mm O/D	
VNZ-03	Vacuum Pick-Up Nozzle 3mm O/D (2.39mm/.094" internal & 3.17mm/.128" external)	
VNZ-03	Vacuum Pick-Up Nozzle 1mm O/D (2.39mm/.03" internal & 1.56mm/.06" external)	
	,	
VNZ-005	Vacuum pick up nozzle 0.5mm OD (.25mm/.010" int. & 1.02-0.76mm/.0403" ext.)	
FS-APR	PCB Support Finger Short (4 included)*	
FSS-APR	PCB Support Finger Short (8 included)**	
FSL-APR	PCB Support Finger Short (4 included with APR-5000, 8 with APR-5000-XLS/XL)	
UBS-APR	Under Board Support*	
UBS-APR-XL	Under Board Support**	
APR-TC3	Colour Fine Gauge Thermocouples (includes 3)*	
APR-TC5	Colour Fine Gauge Thermocouples (includes 5)**	
19782	Adjustable BGA Centering Nest**	
20987	Adjustable CSP Centering Nest	
20534	Squeegee Blade Holder for Printing	
APR-TAB	XY Table***	
SOFT-APR-5000-DZ	Installation Software*	
SOFT-APR-5000-XL	Installation Software**	
APR-XL-PHNK	Pre-Heater Nozzle Kit** includes: Software, Pre Heater Nozzle 50mm, Pre Heater	
	Nozzle 45mm, Pre Heater Nozzle 35mm, Pre Heater Nozzle, Base	
Optional Accessories		
FS-APR-2	PCB Support Finger Short (Pack of 2)	
FL-APR-2	Large PCB Support Finger Long for PCBs from 2.2mm to 6mm (Pack of 2)	
FSL-APR-2	PCB Spring Support Finger Long (Pack of 2)	
FSS-APR-2	PCB Spring Support Finger Short (Pack of 2)	
FLS-APR-2	Large PCB Finger Short for PCBs from 2.2mm to 6mm (Pack of 2)	
FLL-APR-2	Large PCB Finger Long for PCBs from 2.2mm to 6mm (Pack of 2)	
FLSS-APR-2	Large PCB Spring Finger Short for PCBs from 2.2mm to 6mm (Pack of 2)	
FLSL-APR-2	Large PCB Spring Finger Long for PCBs from 2.2mm to 6mm (Pack of 2)	
PF-1	Print Preparation Plate	
VAC-P100	Self-adhesive plates for removal of non-uniform components	
APR-LRK	PCB Large Rail Kit (for use on APR-5000-DZ) - Fits boards up to 12" x 12" (30.5cm x 30.5cm)	
APR-TAB	XY board holder and placement table for APR-5000-DZ	

Technical Specifications

	TECHNICAL SPECIFICATIO	NS
	APR-5000-DZ/-TAB	APR-5000-XLS/-XL
Input Voltage	200 - 240 VAC	200 - 240 VAC
	50/60 Hz	50/60 Hz
	20 Amp Single Phase	25 Amp Single Phase
Power Consumption:		
System Total	2600 W	5100 W
Pre-Heater:		
Inner Zone	900 W	1400 W
Outer Zone	1800 W	2800 W
Reflow Heater	550 W	550 W
Temperature	Closed-Loop Control	Closed-Loop Control
Control Type	(RTD Sensors)	(RTD Sensors)
Maximum Source Temperature:		
Reflow Head	400°C (752°F)	400°C (752°F)
Pre-Heater	350°C (662°F)	350°C (662°F)
Airflow Control	Pre-Set to 8,16 &24 I/min,	Pre-Set to 8,16 &24 I/min
Supply	Self-Contained Pump	Self-Contained Pump
Nitrogen Input	Standard Feature	Standard Feature
(requires 65psi or 4.6 bar)	(requires 65psi or 4.6 bar)	
Component Handling		
Maximum Size	49 mm x 49 mm (1.9" x 1.9")	40 x 40 mm (1.6" x 1.6") XL,
		55 mm x 55 mm (2.16" x 2.16") XLS
Minimum Size	0.51 x 0.25 mm (0.020" x 0.010")	0.51 mm x 0.25 mm (0.020" x 0.010")
Maximun Weight	55g (1.94oz)	55g (1.94oz) or 84g (3oz) with VNZ-19
PCB Handling Capability	ХхY	
Standard	381 mm x 197 mm (15" x 7.75")	622 mm x 622 mm (24.5" x 24.5")
With optional large rail kit APR-LRK	381 mm x 273 mm (15" x 10.75")	Not available
Rework Area	ХхY	
Head Adjustment	228 mm x 197 mm (9" x 7.75")	622 mm x 622 mm (24.5" x 24.5")
Aligned inner	165 x 165 mm (6.5" x 6.5")	445 mm x 445 mm (17.5" x 17.5")
preheater and reflow heater	not suggested without XY table	
Maximum Thickness	6 mm (0.25")	6 mm (0.25")
XY Table	Standard on APR-5000-DZ-TAB-ML	Not available
	Optional on APR-5000-DZ-ML	
Vision		
Maximum Field of View	40mm x 40mm (1.6" x 1.6")	55mm x 55mm (2.2" x 2.2")
Optional Split Field (APR-5000-XLS)	Not available	Corner crossover on large component
System Dimensions W x D x H	483 x 762 x 762 mm	914 x 914 x 838 mm
	(19" x 30" x 30")	(36" x 36" x 33")
Weight	60 kg (130 lbs)	100 kg (220 lbs)
System Warranty	1 Year (Excluding Consumables)	1 Year (Excluding Consumables)
Agency Approvals	CE, cETLus	CE, cTUVus, GS

Other Accessories	
APR-MRS-DEMOPCB	Demonstration PCB
APR-MRS-DEMOKIT	Demonstration PCB Kit with BGA, LGA and other components (see list below)

List of components included with the APR-MRS-DEMOKIT:

- 5 x res, zero Ohm, 0201SMR-PA-10K-0
- 5 x res, zero Ohm, 0402SMR-PA-10K-0
- 5 x res, zero Ohm, 0603SMR-PA-10K-0
- 5 x micro SMD, 4 bump, 0.5 mm pitch
- 5 x micro SMD, 5 bump, 0.5 mm pitch
- 5 x micro SMD, 8 bump, 0.5 mm pitch
- 5 x micro SMD, 10 bump, 0.5 mm pitch
- 5 x LLP LDA16A
- 5 x LLP, plastic, Quad 4x4x0.75 mm body,16LD, 0.5 mm pitch
- 5 x LLP, plastic, Quad 5x4x0.75 mm body 24LD, 0.5 mm pitch

- 4 x PBGA 27 mm 256 balls, 1.27 mm pitch
- 3 x PBGA 17 mm 256 balls, 1.0 mm pitch
- 1 x PBGA 35 mm 388 balls, 1.27 mm pitch
- 1 x POP Bottom 305 balls 12 mm, 0.5 mm pitch
- 1 x Top of POP 128 balls 12 mm, 0.65 mm pitch
- 4 x CVBGA (thin BGA) 97 balls 5 mm, 0.4 mm pitch
- 4 x LGA/MLF100 pin 12 mm fine pitch, 0.4 mm pitch
- 4 x PLCC 44 pin 16 mm, 1.27 mm pitch
- 4 x QFP 44 10 mm by 10 mm, 0.8 mm pitch
- 4 x QFP 100 14 mm by 20 mm, 0.65 mm pitch
- 4 x CTBGA 228 12 mm by 12 mm, 0.5 mm pitch
- 5 x LLP, plastic, Quad 7x7x0.75 mm body 44LD, 0.5 mm pitch 1 x fusion pack (combination 116 QFN & 100 QFP in one package .4 mm pitch)

MRS-1100A Modular Rework System



The MRS-1100A Modular Rework System is an integrated convection rework system for the removal and reflow of BGA/CSP and SMT components.

The MRS-1100A is comprised of a hand held convection tool, preheater, adjustable tool holder, and free-standing board holder to create a manually assisted rework system. A series of nozzles, targeting a variety of applications, and optional light magnifier round out the product offering for this system.

With standard features such as programmability, a digital display, program storage of up to 50 profiles, this system is not only versatile, but also easy and efficient to work with. A choice of board holders and accessories are available that make the system capable of handling multiple sizes of PCBs.

The MRS-1100A allows you the choice of using either the embedded profiling capability that can be configured to operate at a fixed temperature, or a four zone programming option. The unit also allows the temperature to be controlled either at the heat output (internal) or at the board (external). The "external" control function uses a thermocouple which can be placed on the board or a component.

Key Features & Benefits

- Digital display for repeatable temperature settings and profile control
- Automatic control of the preheater for simple operation
- Easy profile creation for operator repeatability
- Integrated vacuum pickup for easy component removal
- Hand held or tool holder mounted for operator comfort
- Manual mode for quick setup
- External thermocouple for process setup and verification
- Digital controlled airflow for repeatable results
- X, Y, Z and Theta controls for component alignment
- Adjustable PCB holder for easy change outs
- Automatic vacuum lift off at the end of the cycle
- Password lockout of programmed profiles

The 4 components of the MRS-1100A are:

- HCT-1000 Programmable Hand Held Convection Tool.
- 2. PCT-1000 Programmable Pre-heater.
- 3. ATH-1100A Adjustable Tool Holder.
- 4. BH-2000 Free standing board holder.

Part No.	Description
MRS-1100A	Modular Rework System

The 4 components of the MRS system can also be ordered separately.

HCT-1000 Programmable Hand Held Convection Tool



The HCT-1000 is a fully Programmable Hand Held Convection Tool offering fast and easy removal and placement of SMT components.

The HCT-1000 stands out as a versatile convection rework tool. It can be used on its own or as part of the MRS-1100A Modular Rework System for more complex applications.

The system comes equipped with a 5mm nozzle and nozzle adapter. In addition, a wide range of nozzles is available.

Key Features & Benefits

- Integrated vacuum pickup for easy component removal
- Profile creation for operator repeatability and storage for up to 50 user defined profiles
- Manual mode for quick setup
- External thermocouple for process setup and verification
- Hand-piece controls for heater and vacuum
- IProgrammable, digitally controlled airflow for repeatable results
- Multiple modes of operation: manual, 4 zone heating (with the MRS-1100A System)
- The HCT-1000 is connected to the PCT-1000 via a cable when used as part of the MRS System
- May be used with ATH-1100A Adjustable Tool Holder

Technical Specifications


Size	229 x 178 x 152mm (9" x 7" x 6 ")
Weight	5.4kg (12 lbs.)
Rated Power	600 W
Input Voltage	100-240 VAC, 50/60 Hz
Storage	0°C to 50°C Temperature
	(32°F to 122°F)
Air Flow	5-25 l/minute
Source Temperature Range	Up to 450°C (840°F)
Vacuum Pump	15" Hg (381mm Hg)
Noise Level	<55 dB

Part No.	Description	
HCT-1000	Programmable Hand Held Convection Tool	
Includes:		
HCT-PS1000	HCT-1000 Power Supply	
HCT-HV1	Hand-piece with integral vacuum, cord and	
	connector	
HCTA-VC-KIT	Vacuum Cup kit, one of each * (see below)	
HCTA-TH1	Hand-piece Tool Holder	
HNA-1	Nozzle Adapter	
HCTA-NW1	Nozzle Wrench	
AC-TCK-36-36	Thermocouple 36 AWG, pack of 2	
HCTA-CC	Communications Cable 4ft	
HN-J0005	5mm Ø nozzle	

Accessories



HCT-1000 Programmable Hand Held Convection Tool





A series of 14 Nozzles are available for use with the MRS-1000 / HCT-1000. The nozzles fit applications reworking components of all sizes from (including, but not limited to) BGAs, QFPs, LGAs, PLCC and SOIC. A custom nozzle program is also available.

Nozzle Measurement and Selection

The nozzle part number (the digits after the "B") represents the size of the component. 2mm have been added to each side of the internal nozzle dimension to allow for component access.

Part Number	Component Size	Components
HN-B0707 ¹	7mm X 7mm	CSP, LGA44
HN-B1010 ¹	10mm X 10mm	CSP, LGA178, LCC28
HN-B1414 ¹	14mm X 14mm	CSP, QFP, TQFP100
HN-B1408 ²	14mm X 8mm,	CSP, SOIC24M
HN-B1515 ³	15mm X 15mm	BGA
HN-B1818 ³	18mm X 18mm	PLC44, CSP, TQFP100, BGA
HN-B2525 ³	25mm x 25mm	BGA, PLCC68
HN-B1809 ⁴	18.2mm X 8.5mm	SOLJ28, SOIC28M, TSOP32
HN-B2519 ⁴	24.5mm X 18.5mm	QFP100, QFP80
HN-B2727 ⁵	27mm X 27mm	BGA
HN-B3232 ⁵	32mm X 32mm	BGA
HN-B3535 ⁵	35mm X 35mm	BGA
HN-B4040 ⁵	40mm X 40mm	BGA
HN-J0005 ⁶	5mm Ø Diameter	DISCRETE

Nozzle Accessories

HCT-NC	7	Nozzle Carrier
HNA-1	8	Nozzle Adapter
HCTA-NW1	9	Nozzle Wrench





Metcal offers a full custom program for nozzles not available within the standard offering shown above. Please contact us: www.metcal.com

PCT-1000 Programmable Pre-heater



The PCT-1000 is a fully Programmable Pre-heater offering more heat, lower temperatures for faster and higher quality results.

The PCT-1000 provides users exceptional ability to increase heat capacity with highly controlled thermal output.

The PCT-1000 can be used as a stand alone unit or as part of the MRS-1000 Modular Rework System.

Key Features & Benefits

- Adds heat capacity and enables lower process temperatures
- Used in a variety of processes including soldering, desoldering, SMD rework
- Provides faster production rates while lowering overall process temperatures.
- 2 modes: manual for constant heater temperature and profile for greater control
- ▶ 4 programmable heating zones and 1 cooling zone
- Storage for up to 50 user defined profiles for easy set-up
- Heater control with temperature controlled either at the heater output or at the board
- High efficiency vortex heater design maximizes ramp to temperature for increased productivity

Part No.		Description
PCT-1000	1	Programmable Preheater
Includes:		
PCT-FS1	2	PCT-1000 Foot Switch
AC-TCK-36-36	3	Thermocouple 36 AWG, pack of 2

Size	330 x 203 x 76mm (13" x 8" x 3")
Weight	3.4kg (7.5 lbs)
Rated Power	1200 W
Input Voltage	100-240 VAC, 50/60 Hz
Storage Temperature	0°C to 50°C
	(32°F to 122°F)
Air Flow	19 cfm
SourceTemperature	25°C to 400°C
Range	(77°F to 752°F)
Operational Modes	Setup, Run, Manual,
Active Setup	
Display	LCD 20 x 4 display
segments	
Number of Programs	50 memory locations
Number of Zones	5 (4 Heat Zones, 1 Cool
	Down Zone)






Adjustable Tool Holder Light Magnifier & Board Holders

ATH-1100A Adjustable Tool Holder LM-1000A Light Magnifier



- Designed to work with the HCT-1000 or as part of the MRS-1100A System.
- Duses the Advanced Head Assembly which features 4" of Z axis adjustment, $\frac{1}{2}$ " fine adjustment of the X & Y axis as well as 30° θ adjustment.
- Features locking hand-piece retainer, Z axis stop and mounting configurations for stand-alone operation or integrated as part of the MRS-1100A.
- Sturdy and easy to attach to the PCT-1000 Programmable Preheater when incorporated into the MRS System.
- Can be attached to the PCT-1000 or used as a standalone unit

Add on



- Integrated light and magnifier
- Features a 4x magnification lens and an integrated
 LED lighting system for shadow free illumination
- LM-BP base plate included



Magnification	4x
Lighting	8 LEDs, white
Power	24V DC
Lens Size	90mm diameter
ESD Safe	



ATH-BASE Optional Base plate for ATH-1100A when used as a standalone unit.

Board Holders



BH-2000

The BH-2000 is a free-standing board holder that provides a solid and stable base for a variety of PCB's. The unit features easily adjustable rails to accommodate boards 8" (203mm) x 12" (305mm).







BH-100 Board Holder. Recommended for use with the PCT-100 Pre-heater

BH-010 Integrated Boardholder for PCT-100







BH-1000 Post-Rail Board Holder. Includes: 4 posts, 2 rails with sliding clips, 4 support pins and flat-head support







BH-PK1000 Board Holder Pin Kit. Includes: 2 discs,2 long pins, 2 short pins

PCT-100 Focused Convection Pre-heather



Key Features & Benefits

- For hand soldering, through-hole desoldering, hot air SMT rework, lead-free, multi-layer boards and assemblies with large ground planes
- Improved process time and exceptional control of potentially damaging temperatures
- Vented top plate allows the PCB to be placed directly over the heater for maximum heat transfer
- Integrated or stand-alone board holder
- Optional adjustable-angle arm rest





The PCT-100 is a focused convection pre-heater that is designed to **provide extra heat capacity** for demanding applications.

Unlike conventional pre-heaters, the PCT-100 Focused Convection Pre-heater directly targets the underside PCB providing a substantial thermal boost for lead- free processes.

Part No.		Description
PCT-100-11	1	Pre-heater 115V
PCT-100-21	1	Pre-heater 230V
PCT-101-11	2	Pre-heater 115V with Arm Rest
PCT-101-21	2	Pre-heater 230V with Arm Rest
PCT-102-11	0	Pre-heater 115V with Arm Rest and
	3	Boardholder
PCT-102-21	0	Pre-heater 230V with Arm Rest and
	3	Boardholder
PCT-103-11		Pre-heater 115V with Arm Rest and
		Integrated Boardholder
PCT-103-21		Pre-heater 230V with Arm Rest and
		Integrated Boardholder
PCT-1HE-11		Heating Element Replacement for
		PCT-100 115V
PCT-1HE-21		Heating Element Replacement for
		PCT-100 230V
BH-010		Integrated Boardholder for PCT-100
		(see page 40)
BH-100	4	Boardholder for PCT-100
PCT-AR	5	Arm Rest for PCT-100

Input Voltage	115 V (PCT-100-11) 230 V (PCT-100-21)
Heater Rating	450 W
Storage Temperature	-10°C-60°C
	(14°F—140°F)
Environmental Temperature	0°C-40°C
	(32°F-104°F)
Air Flow	0.2 CFM (280 l/min)
Control Temperature	Variable up to 300°C
	(572°F)
Surface Resistivity ESD	$10^6\Omega$ - $10^{11}\Omega$
Dimensions (L x W x H)	205 x 155 x 65 mm
	(8" x 6.1" x 2.6")
Weight	1.6 kg (3.5 lbs)
Certificate/Approvals	cTUVus, CE

HCT-900 Hand Held Convection Tool



Key Features & Benefits

- Versatile Hot Air Tool for soldering and desoldering applications
- Robust and compact design
- Analog controls for both airflow and heat
- Closed loop feedback circuit controls the temperature
- Unique low noise air pump (less than 45 db) provides precise airflow control
- Fully ESD compliant

The HCT-900 Hand Held Convection Tool offers a **low cost**, **versatile rework solution** for a wide variety of production and rework application challenges:

- Rework a wide range of simple and complex SMT components
- Rework pin in-hole devices such as sockets and connectors
- Remove solder shorts and splashes by using it with solder braid and flux
- Plastic applications such as applying shrink wrap to components



Part No.	Description
HCT-900-11	115V Hand Held Convection Tool
HCT-HE-11	Heating Element, Replacement, 115V
HCT-900-21	230V Hand Held Convection Tool
HCT-HE-21	Heating Element, Replacement, 230V




HCT-900 Hand Held Convection Tool

Nozzle Selection

The HCT-900 is supplied with a standard single jet H-D50 (0.2", 5.0mm) nozzle. In addition, two rework nozzle kits, predefined for specific applications, are available, as well as a full selection of nozzles.

NZKT-1	Nozzle Kit for Chip Resistors, SOIC & TSOP Packages. Includes (one each):		
	· H-D25		
	· H-SOJ40		
NZKT-2	Nozzle Kit for PLCC, QFP & BQFP packages. Includes (one each):		
	· H-P20 · H-P44 · H-P84		
	· H-Q1420 · H-Q2626		





Input Line Voltage	230 V HCT-900-21 / 115V HCT-900-11
Power	320 W
Air Pump Type	Diaphragm
Air Flow	6-25 l/min
Control Temperature	100°C - 500°C (212°F - 932°F)
Dimensions (L x W x H)	210 x 170 x 140 mm (8.7" x 6.7" x 5.5")
Noise Level	Less than 46 dBA
Surface Resistivity	Unit: $10^5\Omega$ - $10^6\Omega$. Hand-piece & tube: $10^7\Omega$ - $10^{11}\Omega$
Weight	4.7Kg (10.4 lbs)
Certification / Approvals	cTUVus, CE

Portable Fume Extraction Systems

BVX-100 Benchtop Single User Arm/Plenum System

Key Features & Benefits

- Low noise unit
- Portable, single user fume extraction system
- No external ducting or compressor needed
- Unit easily fits on any bench-top or under-bench
- Innovative adaptor transforms the plenum into an arm
- Powerful 85m³/hr-airflow rate
- Immediate extraction of fumes, particles and vapors
- Two filtration configurations: heavy soldering and light dust or light duty organic solvent and adhesive applications
- Bi-coloured LED light indicates when the filters are blocked and require replacing

and require replacing			
Part No.	Description		
BVX-101	Bench-Top, single user arm/plenum system, Pre-HEPA-Gas		
BVX-103	Bench-Top, single user arm/plenum system, Pre-Gas		
Filters			
FG-BVX	Deep Bed Gas Filter		
FM-BVX	Main Filter (Combined HEPA/Gas)		
FP-BVX	Pre-Filter (Pack of 5)		
Accessories	;		
BILLY VDT	Ponlacoment Arm To Planum Adapter		

BVX-ADT	Replacement Arm-To-Plenum Adaptor
BVX-IADT	Inverted Arm Adaptor, ESD Safe
BVX-BCK	Under Bench Mounting Bracket
BVX-CH01	Connection hose, 50mm (2") diameter, 1.8m (6")

Table bracket with 2 C-clamps



BVX-TB01



Technical SpecificationsStatic Pressure (suction force)

110		
	0	
		1
	1	-

Filters are easy to remove and replace.

Fan Capacity	110m ³ /h (65 cfm)	250m ³ /h (150 cfm)
Flow Rate (with filter)	85m³/h (50 cfm)	2 x 75m ³ /h (45 cfm)
Air Inlets/Number of Stations	1	2
HEPA Efficiency	99.97% at 0.3 micron	99.97% at 0.3 micron
Noise Level	< 55 db A	< 55 db A
Dimensions (W x D x H)	300mm x 230mm x 290mm (11.8" x 9.1" x 11.4")	508mm x 254mm x 388mm (20" x 10" x 15.3")
Weight	9kg (20lbs)	9kg (20lbs)
Voltage	100-240 VAC	100-240 VAC
Frequency	50-60 Hz	50-60 Hz
Power	85 watt	85 watt
Certification	UL, CSA, CE	UL, CSA, CE

1250 Pa (5"WC)

BVX-200 Two Stations Portable Filter Unit

Key Features & Benefits

- Two station design for dynamic fume extraction
- New brushless motor, quiet operation
- Complete portability, placed under or next to the bench-top
- ▶ Fitted with 2x 50mm (2") Ø arms or 1x 63mm (2.5") Ø arm
- Main filter has a HEPA efficiency of 99.97% at 0.3 micron, and an activated carbon filter to remove additional gases
- Deep-bed gas filter for high capacity of gas filtration, such as cleaning with solvents or conformal coatings
- Audible alarm informs operators when filters need replacing
- Easy access on/off remote switch

	0.0
Part No.	Description
BVX-201	Filter unit for 2 stations, Pre-HEPA-Gas
BVX-203	Filter unit for 2 stations, Pre-Deep Bed Gas
BVX-201-KIT	Filter unit with 2 BVX-ARML, Pre-HEPA-Gas
BVX-201-KIT1	Filter unit with 2 BVX-ARM-K1, Pre-HEPA-Gas

i iitei s		
FP-BVX200	Pre-Filter (Pack of 5)	
FM-BVX200	Main Filter HEPA Carbon	
FG-BVX200	Deep Bed Gas Filter	

BVX-ARM 760mm (30") with 1.8m (6') long hose &
table bracket w/ C-clamps
BVX-ARM 760mm (30") & table bracket w/ C-clamps
Arm flexible ESD safe, 760mm (30")
Arm flexible ESD safe, 1.5m (59") with arm clip
Table bracket with 2 C-clamps
Connection hose, 50mm (2") diameter, 1.8m (6')
Connection hose, 50mm (2") diameter, 3.6m (12')
Remote power switch (for use with BVX-200 only)

850 Pa (3.5"WC)

3.6 m (12') Max duct run

Multi-function Extraction Systems

MFX-2200C Particle Fume Extraction System

The multi-user MFX-2200C Fume Extraction System provides the ultimate performance in a compact size that easily fits under most workbenches. It is ideal for removing solder fumes and filtering laser fumes.

Key Features & Benefits

- Excellent air flow performance
- Large, pleated pre-filter
- ▶ HEPA filter rating of 99.97% at 0.3 micron
- Casters as standard
- Dust filter seal keeps filter housing clean
- Minimum operating noise
- Compact size, unit fits under most workbenches
- Connects up to 4 Omniflex arms with rectangular nozzle (EA1122) or large hood (EA1126)
- Connects up to 8 BVX arms or 8 Omniflex arms with tapered nozzle (EA1124)

Part No.	Description
MFX-2200C-A	Particle Fume Extraction System Analog 110V
MFX-2206C-A	Particle Fume Extraction System Analog 230V
MFX-2200C-D	Particle Fume Extraction System Digital 110V
MFX-2206C-D	Particle Fume Extraction System Digital 230V
Filters	
FIL22P030	Prefilter Pleated 60% Efficiency (Pack of 2)
FIL22H070	Combination Filter HEPA/Carbon
Accessories	
AC2204	Top cover with 2 air inlets Ø100mm (4") and 2 air inlets Ø 63mm (2.5")

Technical Specifications

	110V Units	230V Units
Air Inlet Openings	4 x Ø2.5"	4 x Ø63mm
Fan Capacity	600 cfm	900m³/h
Flow Rate	400 cfm	600m³/h
HEPA Efficiency	99.97% at 0.3 micron	99.97% at 0.3 micron
Static Pressure	4.5" WC Max	1075 Pa
Power Supply	100-120VAC, 60Hz	220-240VAC, 50Hz
Power	400 Watt	400 Watt
Noise Level	58 dbA	58 dbA
Dimensions (W x D x H)	17.7" x 20.7" x 26.4"	450 x 525 x 670mm
Weight	93 lbs	43 Kg
Certification	UL, CSA	CE
Max duct run	100'	30 m

Controls and Filter Monitor

- Unit On/Off Switch with power indicator
- Thermal overload protection
- Analog models with filter status gauge
- Digital models with filter status indicator lights and other control options

MFX-2200G Gas Fume Extraction System

The MFX-2200G Fume Extraction System has been specifically designed for the removal of gases and vapors from a range of heavy duty bench-top applications, including solvent cleaning, gluing/bonding and conformal coatings.




Key Features & Benefits

- High capacity gas filter cartridge ensures a long dwell-time of the gases inside the filter media
- Large, pleated pre-filter
- Casters as standard
- Minimum operating noise
- Provides air flow for two exhaust cabinets
- The unit lid features 100mm (4") and 63mm (2.5") air inlet flanges suitable for the connection of exhaust arms or cabinets

Part No.	Description
MFX-2200G-A	Gas Fume Extraction System Analog 110V
MFX-2206G-A	Gas Fume Extraction System Analog 230V
MFX-2200G-D	Gas Fume Extraction System Digital 110V
MFX-2206G-D	Gas Fume Extraction System Digital 230V
Filters	
FIL22P040	Prefilter Pleated 85% Efficiency
FIL22P040 FIL22G010	Prefilter Pleated 85% Efficiency Gas Filter Cartridge 11kg (25lbs)
	<u> </u>
FIL22G010	Gas Filter Cartridge 11kg (25lbs)

	110V Units	230V Units
Air Inlet Openings	2xØ4" & 2xØ2.5"	2xØ100mm & 2xØ63mm
Fan Capacity	600 cfm	900m³/h
Flow Rate	350 cfm	550m³/h
Static Pressure	4.5" WC Max	1075 Pa
Power Supply	100-120VAC, 60Hz	220-240VAC, 50Hz
Power	400 Watt	400 Watt
Noise Level	58 dbA	58 dbA
Dimensions (W x D x H)	17.7" x 20.7" x 26.4"	450 x 525 x 670mm
Weight	115 lbs	52 Kg
Certification	UL, CSA	CE
Max duct run	100'	30 m





Omniflex & BVX Arms



The **Omniflex Arms** (Ø63mm) are designed for higher airflow rates and effective fume capture from greater distances. A unique ball/socket design provides an unmatched flexibility in manoeuvring and positioning. The arms can be adjusted in working length or radius, simply by adding or removing Omniflex components. ESD conformance is ensured through the use of fully conductive material.

Key Features & Benefits

- 140m³/h (85cfm) air flow rating (varies with nozzle)
- ▶ 63mm (2.5") diameter
- ▶ 0.6m (24") long with optional extensions of 300mm (12")





Part No.		Description
EA1122	2	Omniflex Arm ESD with Rectangular Nozzle
EA1124	3	Omniflex Arm ESD with Tapered Nozzle
EA1126	1	Omniflex Arm ESD with Large Hood 350 x 212mm (14" x 8.5")
Q-AD426530		Replacement nozzle - Rectangular
Q-AD426550		Replacement nozzle - Tapered
Q-AD426560		Replacement nozzle - Large Hood
AC1101	4	Damper for Omniflex Arm
AC1102		Omniflex Arm Extension 30cm (12")

*BVX-200 series is only rated for one EA1122 arm, one EA1126 arm or two EA1124 arms.



The **BVX Arms** (Ø50mm) are most economic solution while providing good airflow rates and high flexibility. The spiral rolled duct can be tightened in stiffness and can be positioned precisely. The BVX Arm-K2 kit includes a mounting plate and c-clamps for universal mounting. A Y-connection piece is available to connect two BVX Arms to one hose.

Key Features & Benefits

- > 75m³/h (45cfm) air flow rating
- ▶ 50mm (2") ducting with 40mm (1.75") nozzle
- 760mm (30") long
- BVX Arms compatible with all units



Part No.	Description
BVX-ARM-K1	1 BVX-ARM 760mm (30") long with 1.8m (6') long hose and
	table bracket with C-clamps
BVX-ARM-K2	1 BVX-ARM 760mm (30") long and table bracket with C-clamps
BVX-ARM	Arm flexible ESD safe, 760mm (30") long
BVX-ARML	Arm flexible ESD safe, 1.5m (59") long with arm clip

Connection Hoses for Omniflex and BVX Arms

CH0251	6	Connection Hose 2.5m xØ63mm (8" x 2.5") with clamps
CH0252	6	Connection Hose 3.5m xØ63mm (12" x 2.5") with clamps
CH0253	6	Connection Hose 7.5m xØ63mm (25" x 2.5") with clamps
AC2025	7	Y-Piece for Ø63mm (2.5") hose with clamps

Tip Extraction & Exhaust Cabinet

BTX-208 Portable Tip Extraction Unit

Key Features & Benefits

- ▶ High performance extraction directly from the tip of any iron
- ▶ Easy extraction network configuration for up to 8 benches
- ▶ Complete portability. Designed for under-bench installation
- Main filter has a HEPA efficiency of 99.97% at 0.3 micron, and an activated carbon filter to remove gases
- ▶ Both pre- and main- filters can be changed independently
- Plug-and-play ducting system for simple, flexible low cost solution and fast installations
- Universal hose connection kit

Part No.	Description
BTX-208	Filter Unit for 8 Tip Extraction Stations, Pre/HEPA/Gas
Filters	
FP-BVX200	Pre-Filters (pack of 5)
FM-BVX200	Main Filter, HEPA 99.95% / Carbon

Iron Adapter Kits

AC-FX1	Universal tip extraction
	iron adapter clip



CONNECTION KITS:

BTX-CK2-25	Connection Kit for 2-4 stations with 2.5m (8') Long Hose
BTX-CK4-50	Connection Kit for 4-8 stations with 5m (16') Long Hose
BTX-CK4-75	Connection Kit for 4-8 stations with 7.5m (25') Long Hose

Individual Parts

CH0121	1	Flexible Hose Ø35mm x 2.5m (8') Long
CH0122	1	Flexible Hose Ø35mm x 5m (16') Long
CH0123	1	Flexible Hose Ø35mm x 7.5m (25') Long
AC-TX001-4	2	Couplings with 2 Glands 5.6mm (pack of 4)
18566S-5	3	End Plug (Pack of 5)
AC-TX002-2	4	T-Piece Connector (pack of 2)
19115S-10	5	Pipe Clip (pack of 10)

	CONNECTION KITS		BTX-CK2-25	BTX-CK4-50	BTX-CK4-75
	Max number of stations	single-row bench	2	4	4
	when using 5.6mm tubes	double-row bench	4	8	8
			Qty	Qty	Qty
1	Flexible Hose Ø35mm (1.25	")	2.5m (8")	5.0m (16")	7.5m (25')
2	Coupling with 2 Glands 5.6n	nm 2	4	4	
3	End Plug		1	2	2
4	T-piece Connector		0	1	1
5	Pipe Clip		2	5	5
-	Roll of Vinyl Tape		1	1	1

Technical Specifications

Max. number of stations	8
Flow Rate per station	>28 l/min
Noise Level	< 55 db A
Dimensions (W x D x H)	508mm x 254mm x 388mm (20" x 10" x 15.3")
Weight	9kg (20lbs)
Voltage	100-240 VAC
Frequency	50-60 Hz
Power	85 Watt
Max Duct Run	30m (100')
Certification	UL/CSA/CE





EC1800 Exhaust Cabinet

The EC1800 is an ideal bench top exhaust cabinet for applications such as volatile vapors and gases with high toxic levels.

A hinged and clear viewing panel maintains excellent visibility while at the same time reducing the airflow demand on the cabinet.



Key Features & Benefits

- ▶ Bench Top exhaust cabinet
- Offers operators high levels of protection
- Easy Assembly
- Dimensions (W x D x H) 760 x 510 x 560mm (30" x 20" x 22")
- ▶ Connection Flange Ø100mm (4")
- Requires MFX-2200G-A/D Gas Fume Filtration System

Part No.	Description
EC1800	Exhaust Cabinet with clear viewing panel
CH0047	Connection hose 2.5m (8') Long Ø100mm (4") with Clamps

DX-250 /-350 Digital Dispensers

DX-250 Series Digital Dispenser



The DX-250 Series is a high performance Digital Dispenser. Complete with a range of accessories, the micro-air dispensing system unites affordability with high accuracy and repeatability for exceptional results.

These user friendly fluid dispensing systems include a digital timer with a rotary control time knob for easy setup and a vacuum suck-back control for all viscosities of fluids.

Key Features & Benefits

- Small footprint and lightweight
- Economical dispenser
- Highly accurate and repeatable micro-air dispensing
- Digital timer and vacuum controls
- Available in two versions of operating pressure: 0 to 100 psi for general applications, and 0 to 15 psi for specific low viscosity applications
- Packaged ready to use with a universal power supply, foot switch, air hose, sample tips, syringe barrels and adapter.
- ► I/O Interface for robotic applications

Part No.	Description
DX-250	Digital Dispenser 0 to 100 psi (0 to 6.9 bar)
DX-255	Digital Dispenser 0 to 15 psi (0 to 1.0 bar)

Technical Specifications

Size (W x L x H)	152mm x 165mm x 178mm (6" x 6.5" x 7")
Weight	1.2Kg (2.6 lb)
Cycle Rate	600 cycle/minute
Timing Range	0.020 to 60.000 seconds
Timing Tolerances	+/- 0.001%
Input Voltage	100-240 VAC
Input Frequency	50-60 Hz
Cycle Mode	TIMED, PURGE
I/O Interface	Initiated by voltage or contact closure
Certification	CE, TUV-GS, NRTL
Warranty	1 year





DX-350 Series Digital Dispenser

The DX-350 Series is a microprocessor-driven and fully digital Dispenser. Intuitive to use, the DX-350 dispenses low, medium and high-viscosity fluids accurately and consistently.



The firmware provides the option of programming up to 10 varied, sequenced or individual shots.

The DX-350 includes an adjustable vacuum-driven "suckback" to control material "tailing" and waste.

Key Features & Benefits

- Small footprint and lightweight
- 10 programmable dispense routines and 4 operating modes
- Digital timer, pressure and vacuum read-outs
- Accurate reproduction of sequences of beads or dots
- Adjustable vacuum feature for controlling drips of fluid between dispense cycles
- Available in two versions of operating pressure: 0 to 100 psi for general applications, and 0 to 15 psi for specific low viscosity applications
- Packaged ready to use with a universal power supply, foot switch, air hose, sample tips, syringe barrels and adapter
- I/O Interface for robotic applications

Part No.	Description
DX-350	Digital Dispenser 0 to 100 psi (0 to 6.9 bar)
DX-355	Digital Dispenser 0 to 15 psi (0 to 1.0 bar)

Size (W x L x H)	152mm x 165mm x 178mm (6" x 6.5" x 7")
Weight	1.2Kg (2.6 lb)
Cycle Rate	1200 cycle/minute
Timing Range	0.008 to 60.000 seconds
Timing Tolerances	+/- 0.001%
Input Voltage	100-240 VAC
Input Frequency	50-60 Hz
Memories	10 programmable
Cycle Mode	TIMED, INTERRUPT, TEACH, PURGE
I/O Interface	Initiated by voltage or contact closure
Certification	CE, TUV-GS, NRTL
Warranty	1 year





Dispensing Tips

TE Tips Series



- Stainless-steel cannula with a double Helix polypropylene hub
- Burr-free and electro-polished cannula for unobstructed and consistent material flow
- Silicone and chloride free
- ▶ Sold in packs of 50

Gauge	1/4" (6.35mm)	1/2" (12.7mm)	1" (25.4mm)	1-1/2" (38.1mm)
14		914050-TE	914100-TE	914150-TE
15		915050-TE	915100-TE	915150-TE
18	918025-TE	918050-TE	918100-TE	918150-TE
20	920025-TE	920050-TE	920100-TE	920150-TE
21	921025-TE	921050-TE	921100-TE	921150-TE
22	922025-TE	922050-TE	922100-TE	922150-TE
23	923025-TE	923050-TE	923100-TE	923150-TE
25	925025-TE	925050-TE		
27	927025-TE	927050-TE		
30	930025-TE	930050-TE		
32	932025-TE			
34	934025-TE			

P

TE Bent Tip Series

- Precision bent tips at 45° and 90° angles
- Perfect for dispensing fluid in hard to reach places
- Sold in packs of 50

1/2" (12.7mm)1-1/2" (38.1mm)					
Gauge	90°	45°	45°		
14	914050-90BTE	914050-45BTE	914150-45BTE		
15	915050-90BTE	915050-45BTE			
18	918050-90BTE	918050-45BTE	918150-45BTE		
20	920050-90BTE	920050-45BTE			
21	921050-90BTE	921050-45BTE	921150-45BTE		
22	922050-90BTE	922050-45BTE			
23	923050-90BTE	923050-45BTE			
25	925050-90BTE	925050-45BTE			
27	927050-90BTE	927050-45BTE			
30	930050-90BTE	930050-45BTE			

Color Coding and Gauge For TE Series and TE Bent Tips

 Gauge	Colour	I.D. (inches)	!.D.(mm)
14	Olive	0.063	1.600
15	Amber	0.054	1.371
18	Green	0.033	0.838
20	Pink	0.024	0.610
21	Purple	0.020	0.508
22	Blue	0.016	0.406
23	Orange	0.013	0.330
25	Red	0.010	0.254
27	Clear	0.008	0.203
30	Lavender	0.006	0.152
32	Yellow	0.004	0.102



BT Series

- Double Helix Brush Tips for "spread" applications such as glues and other materials.
- Soft brush is made of Red Sable
- Stiff brush is made of Nylon
- Available in packs of 12.

Gauge	Soft Bristle	Stiff Bristle	
16	916BT-SOFT	916BT-STIFF	
18	918BT-SOFT	918BT-STIFF	
22	922BT-SOFT	922BT-STIFF	



TS-P Plastic Series Tips

- Flexible tips allow access to hard to reach areas
- ▶ 1-1/2" but length can also be customized
- Ideal for CA applications
- Both hub and cannula are made from polypropylene
- ▶ Sold in packs of 50

Gauge	Colour	TS-P Needle
15	Grey	915150-PTS
16	Brown	916150-PTS
18	Pink	918150-PTS
20	Yellow	920150-PTS
22	Black	922150-PTS
25	Red	925150-PTS



TT Series Tips

- Molded in high density polyethylene with UV light block additive
- Include a double Helix luer lock hub
- Tapered tip prevents blockage and increases the flow of high viscosity materials
- Sold in packs of 50

Gauge	Colour	TT Needle
14	Olive	914125-DHUV
16	Grey	916125-DHUV
18	Green	918125-DHUV
20	Pink	920125-DHUV
22	Blue	922125-DHUV
25	Red	925125-DHUV
27	Clear	927125-DHUV



Dispensing Tip Kit

Kit contains a selection of most popular TE, TE Bent and TT tips

900-NK	Dispensing Tip Kit
000 1411	Diopononing rip rat

Dispensing Consumables

NEW



End Caps

- Designed to seal large end of the syringe barrel
- Ensure no contaminants come in contact with material during storage
- Made from polyethylene
- Available in packs of 50

Size	End Cap	
3cc	903-ECB	
5cc	905-ECB	
10cc	910-ECB	
30/55cc	93055-ECB	



Tip Cap

- Use to seal syringe barrel when not in use
- Fits all syringe sizes
- Blue stand up tip cap that enables the syringe barrel to stand upright
- Made from polypropylene
- Sold in packs of 50

900-ORTC	Tip Care Double Helix Thread, Orange
900-BTC	Tip Care Double Helix Thread, Black
900-STC	Stand-up Tip Cap, Blue









Air Powered Pistons

- Wiper Pistons provide a seal for low to medium viscosity fluids
- Straight Wall Pistons for reduced stringing with medium to high viscosity fluids
- ▶ Both styles of pistons are made from polyethylene

▶ Sold in packs of 50

N	$-\mathbf{w}$

Size	Wiper Piston (White)	Straight Wall (Red)	Easy Flow (Blue)
3cc	903-WW	903-SWR	903-EFB
5cc	905-WW	905-SWR	905-EFB
10cc	910-WW	910-SWR	910-EFB
30/55cc	93055-WW	93055-SWR	93055-EFB

	700 Series Color	Application Examples
Smooth Piston	Blue	Anaerobic, epoxy, flux, SMA, oil, silicone, UV
Tighter Piston	White	Any fluid used on a mechanical rod/gun including UV
Straight Wall Piston	Red	SMA, Solder paste, viscous grease

Syringe Assembly Kits

 Packaged together in ready-to-use kits of 50 each (syringe and Wiper Piston, without piston inserted)

Size	Natural
3cc	903-NW
5cc	905-NW
10cc	910-NW
30cc	930-NW
55cc	955-NW





Manual Syringe Barrels NEW

- Provide simple and quick dispensing solutions without the need for compressed air
- Molded from Polypropylene resin, manual plungers
- Compatible with a wide range of dispensing fluids
- Pistons are made from thermoplastic rubber
- Available dry or with lubrication
- Sold in packs of 50



Syringe barrels

- Unique ultra-low draft of inner diameter yield high accuracy and stability
- Industry compliant silicone / chloride free, low friction polypropylene
- 3 colours: Natural for most generic applications, Amber for protection of UV/visible light block (up to 520nm), Black for total light block
- ▶ Sold in packs of 50

Size	Natural	Dark Amber	Black
3cc	903-N	903-D	903-B
5cc	905-N	905-D	905-B
10cc	910-N	910-D	910-B
30cc	930-N	930-D	930-B
55cc	955-N	955-D	955-B

Part No.	Description
903-PL	Manual Plunger, 3cc
903-PRD	Manual Piston Rubber, 3cc
903-PRL	Manual Piston Rubber, Lub, 3cc
905-PL	Manual Plunger, 5cc
905-PRD	Manual Piston Rubber, 5cc
905-PRL	Manual Piston Rubber,Lub, 5cc
910-PL	Manual Plunger, 10cc
910-PRD	Manual Piston Rubber, 10cc
910-PRL	Manual Piston Rubber, Lub, 10cc
930-PL	Manual Plunger, 30cc
930-PRD	Manual Piston Rubber, 30cc
930-PRL	Manual Piston Rubber, Lub, 30cc

Foot Valve Dispenser & Accessories

924-DFV Series Foot Valve Dispenser



The 924-DFV Series Foot Valve Dispenser offers increased production combined with dispenser economy. Floor mounted, they have a built in pressure regulator, pressure gauge and a unique fast-dump, three-way air valve. Output rate and shot size are operator controlled.

The 924-DFV is the ideal basic dispensing unit for most

general applications of adhesives, sealants, coatings and compounds.

The 924-DFV-VAC features a vacuum suck-back to prevent very thin materials from dripping to reduce tailing or stringing with thicker materials.

Key Features & Benefits

- Ideal for applications where electricity is prohibited
- Robust design
- ▶ Floor mounted conserves bench space
- No programming required

Part No.	Description
924-DFV	Foot Valve Dispenser
924-DFV-VAC	Foot Valve Dispenser with Vacuum

Technical Specifications

Size (W x L x H)	124mm x 206mm x 121mm (8.1" x 4.9" x 4.7")
Weight	1.8Kg (4 lb)
Input Pressure	100 psi max (6.9 bar)
Operating Pressure	Up to 100 psi (6.9 bar)
Cycle Mode	Manual
Vacuum Force	Up to 15" of Hg (924-DFV-VAC only)
Warranty	1 year





Receiver Head Assembly

- Connecting link between time/pressure controllers and Syringe assemblies
- Provides a safe connection for accident proof dispensing
- Available with 3 or 6 feet of tubing
- Includes: receiver head with O-ring, tubing and male guick connector
- Receiver heads are made of Delrin®
- Sold individually

Size	3' Hose	6' Hose
3cc	903-3RHB	903-6RHB
5cc	905-3RHB	905-6RHB
10cc	910-3RHB	910-6RHB
30/55cc	93055-3RHB	93055-6RHB

Replacement O-rings for Receiver Head

Sold in packs of 10

Size	EPR O-ring	VITON O-ring
Зсс	P3015EPK	P3019VPK
5cc	P3016EPK	P3020VPK
10cc	P3017EPK	P3021VPK
30/55cc	P3018EPK	P3022VPK




Manual Syringe Gun

- Lightweight barrel applicator gun
- Provides excellent control for medium/high viscosity products
- Easy to use. No dripping or mess

Size	Manual Syringe Gun	Plunger Rod
10cc	910-MSG	71000ROD
30cc	930-MSG	73000ROD

Vacuum Pencil

- Use for pick and place function
- Stand-alone vacuum pick-up requires shop air
- available



TS8120	Vacuum Pick Up Assembly

Syringe Holder

Use for 900 Series syringes

SH-300 Syringe Holder



Finger Switch Assembly

- Use with OKi dispensers and syringes in place of a foot pedal
- Provides control at your finger tip

DX9010 Finger Switch Assembly for DX Series Dispenser





METCAL

is a leading global brand of bench tool solutions delivering the optimal balance of

performance

and reliability for the electronics production assembly.



www.metcal.com

Metcal and OKi are brands of **OKINTERNATIONAL**