

LUXEON Rebel and
LUXEON Rebel ES
Color Portfolio

*Illuminating
your creativity*

Technical Datasheet DS68

LUXEON
NEVER BEFORE POSSIBLE



LUXEON[®] Rebel and LUXEON[®] Rebel ES Color Portfolio

Introduction

With leading light output, color stability, flux density, and clear saturated colors, the LUXEON[®] Rebel Color Portfolio of emitters is ideal for a wide variety of lighting, signaling, signage and entertainment applications. Every LUXEON Rebel Color Portfolio emitter has built-in quality, reliability, lumen maintenance and the ease of manufacturing needed to create a superior high quality light.

Using the information in this document you can begin designing applications to your unique specifications.

Use LUXEON Rebel Color Portfolio to

- deliver more usable light and higher flux density
- optimize applications to reduce size and cost
- tightly pack the LEDs for color mixing
- engineer more robust applications
- utilize standard FR4 PCB technology
- simplify manufacturing through the use of surface mount technology
- recognized under the Component Recognition Program of Underwriters Laboratories Inc. UL listing E327436.

PHILIPS
LUMILEDS

Table of Contents

| | |
|--|----|
| General Product Information | 3 |
| Product Nomenclature | 3 |
| Average Lumen Maintenance Characteristics..... | 3 |
| Environmental Compliance | 3 |
| Flux and Efficacy Performance Characteristics | 4 |
| Flux Performance, Binning, and Supportability..... | 6 |
| Optical Characteristics | 7 |
| Electrical Characteristics..... | 8 |
| Absolute Maximum Ratings | 9 |
| JEDEC Moisture Sensitivity | 9 |
| Reflow Soldering Characteristics | 10 |
| Mechanical Dimensions: LUXEON Rebel Color Emitter | 11 |
| Mechanical Dimensions: LUXEON Rebel ES Color Emitter | 12 |
| Pad Configuration | 13 |
| Solder Pad Design | 13 |
| Wavelength Characteristics..... | 14 |
| Typical Light Output Characteristics over Temperature..... | 15 |
| Typical Forward Current Characteristics | 16 |
| Typical Relative Luminous Flux | 17 |
| Current Derating Curves..... | 19 |
| Typical Radiation Patterns..... | 22 |
| Typical Radiation Patterns..... | 25 |
| Typical Chromaticity Characteristics PC Amber | 26 |
| Emitter Pocket Tape Packaging..... | 27 |
| Emitter Reel Packaging | 28 |
| Product Binning and Labeling | 29 |
| Luminous Flux Bins..... | 30 |
| Forward Voltage Bins..... | 31 |
| Color Bins..... | 32 |
| Color Bins PC Amber | 34 |

General Product Information

Product Nomenclature

LUXEON Rebel color emitters are tested and binned at 350 mA with the exception of LUXEON Rebel ES color emitters which are tested and binned at 700 mA.

The part number designation is explained as follows:

L X M L - A B C D - E F G H

L X M 2 - A B C D - E F G H

L X M 3 - A B C D - E F G H

Where:

A — designates radiation pattern (value P for lambertian)

B — designates color (see LUXEON Rebel color binning and labeling section)

C — designates color variant (0 for color variants)

D — designates test current (value 1 for 350 mA; 2 for 700 mA.)

E — open slot to accommodate additional requirements per product and part number

FGH — minimum luminous flux (lm) or radiometric power (mW) performance

Therefore products tested and binned at 350 mA or 700 mA follow the part numbering scheme:

L X M L - P x 0 1 - x x x x

L X M L - P x 0 2 - x x x x

L X M 2 - P x 0 1 - x x x x

L X M 3 - P x 0 1 - x x x x

Average Lumen Maintenance Characteristics

LUXEON Rebel color emitters are tested and binned at 350 mA and LUXEON Rebel ES color emitters at 700 mA, with current pulse duration of 20 ms. All characteristic charts where the thermal pad is kept at constant temperature (25°C typically) are measured with current pulse duration of 20 ms. Under these conditions, junction temperature and thermal pad temperature are the same.

Philips Lumileds projects that green, cyan, blue and all royal blue LUXEON Rebel color products will deliver, on average, 70% lumen maintenance (B50, L70) at 50,000 hours of operation at a forward current of 700 mA. This projection is based on constant current operation with junction temperature maintained at or below 135°C. Red, red-orange and amber LUXEON Rebel color products will also deliver, on average, 70% lumen maintenance (B50, L70) at 50,000 hours of operation at a forward current of 350 mA and is based on constant current operation with junction temperature maintained at or below 110°C. LUXEON Rebel PC amber delivers, on average, 70% lumen maintenance (L70) at 50,000 hours of operation at a forward current of up to 700 mA. This projection is based on constant current operation with junction temperature maintained at or below 130°C.

This performance is based on independent test data, Philips Lumileds historical data from tests run on similar material systems, and internal LUXEON Rebel reliability testing. Observation of design limits included in this data sheet is required in order to achieve this projected lumen maintenance.

Environmental Compliance

Philips Lumileds is committed to providing environmentally friendly products to the solid-state lighting market. LUXEON Rebel and LUXEON Rebel ES color products are compliant to the European Union directives on the restriction of hazardous substances in electronic equipment, namely REACH and the RoHS directive. Philips Lumileds will not intentionally add the following restricted materials to the LUXEON Rebel Color Portfolio: lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE).

Flux and Efficacy Performance Characteristics

Luminous Flux Characteristics for LUXEON Rebel Color Portfolio, Thermal Pad Temperature =25°C

Table I.

| Color | Part Number | Performance @ 350 mA | | | Performance @ 700 mA | | | |
|-----------------|----------------|--|----------|---|--|--|---|----|
| | | Min Luminous Flux (lm) or Radiometric Power (mW) | Typ Flux | Typ Efficacy (lm/W) or Radiant Efficacy for Royal Blue and Deep Red | Min Luminous Flux (lm) or Radiometric Power (mW) | Typ Luminous Flux (lm) or Radiometric Power (mW) | Typ Efficacy (lm/W) or Radiant Efficacy for Royal Blue and Deep Red | |
| Green | LXML-PM01-0100 | 100 | 102 | 100 | | 161 | 68 | |
| | LXML-PM01-0090 | 90 | 95 | 93 | | 150 | 63 | |
| | LXML-PM01-0080 | 80 | 88 | 86 | | 139 | 58 | |
| | LXML-PM01-0070 | 70 | 79 | 78 | | 125 | 52 | |
| Cyan | LXML-PE01-0080 | 80 | 83 | 81 | | 133 | 56 | |
| | LXML-PE01-0070 | 70 | 76 | 75 | | 122 | 51 | |
| | LXML-PE01-0060 | 60 | 67 | 66 | | 110 | 46 | |
| Blue | LXML-PB01-0040 | 40.0 | 41 | 38 | | 70 | 29 | |
| | LXML-PB01-0030 | 30.0 | 35 | 33 | | 58 | 24 | |
| | LXML-PB01-0023 | 23.5 | 28 | 26 | | 48 | 20 | |
| | LXML-PB01-0018 | 18.1 | 22 | 21 | | 38 | 16 | |
| | LXML-PB02 | | | | | 50 | 58 | 28 |
| | | | | | | 60 | 67 | 32 |
| | | | | | | 70 | 75 | 36 |
| | | | | | | 80 | 83 | 40 |
| Royal Blue | LXML-PR01-0500 | 500 mW | 520 mW | 48% | | 910 mW | 40% | |
| | LXML-PR01-0425 | 425 mW | 480 mW | 44% | | 840 mW | 37% | |
| | LXML-PR02-1100 | | | | 1100 mW | 1120 mW | 53% | |
| | LXML-PR02-1050 | | | | 1050 mW | 1070 mW | 51% | |
| | LXML-PR02-1000 | | | | 1000 mW | 1030 mW | 49% | |
| | LXML-PR02-0950 | | | | 950 mW | 970 mW | 46% | |
| | LXML-PR02-0900 | | | | 900 mW | 940 mW | 44% | |
| | LXML-PR02-0800 | | | | 800 mW | 890 mW | 42% | |
| LXML-PR02-A900* | | | | 900 mW | 1030 mW | 49% | | |

* LXML-PR02-A900 is a selection of color Bins 4,5 only.

Flux and Efficacy Performance Characteristics, Continued

Luminous Flux Characteristics for LUXEON Rebel Color Portfolio, Thermal Pad Temperature =25°C

Table I, Continued


| Color | Part Number | Performance @ 350 mA | | | Performance @ 700 mA | | |
|------------|----------------|--|----------|---|--|--|---|
| | | Min Luminous Flux (lm) or Radiometric Power (mW) | Typ Flux | Typ Efficacy (lm/W) or Radiant Efficacy for Royal-Blue and Deep Red | Min Luminous Flux (lm) or Radiometric Power (mW) | Typ Luminous Flux (lm) or Radiometric Power (mW) | Typ Efficacy (lm/W) or Radiant Efficacy for Royal-Blue and Deep Red |
| Deep Red | LXM3-PD01 | 350 mW | 360 mW | 46% | 720 mW | 42% | |
| | | 300 mW | 320 mW | 41% | 640 mW | 38% | |
| | | 260 mW | 290 mW | 37% | 580 mW | 34% | |
| Red | LXM2-PD01-0060 | 60 | 62 | 83 | 119 | 74 | |
| | LXM2-PD01-0050 | 50 | 53 | 75 | 106 | 65 | |
| | LXM2-PD01-0040 | 40 | 48 | 65 | 90 | 56 | |
| | LXML-PD01-0050 | 50 | 52 | 53 | 85 | 35 | |
| | LXML-PD01-0040 | 40 | 46 | 47 | 75 | 30 | |
| | LXML-PD01-0030 | 30 | 38 | 37 | 62 | 24 | |
| Red-Orange | LXM2-PH01-0070 | 70 | 72 | 98 | 134 | 83 | |
| | LXM2-PH01-0060 | 60 | 67 | 91 | 122 | 76 | |
| | LXML-PH01-0060 | 60 | 62 | 63 | 100 | 40 | |
| | LXML-PH01-0050 | 50 | 56 | 57 | 90 | 35 | |
| PC Amber | LXM2-PL01-0110 | 110 | 112 | 105 | 198 | 96 | |
| | LXM2-PL01-0100 | 100 | 102 | 96 | 184 | 83 | |
| | LXM2-PL01-0090 | 90 | 95 | 89 | 171 | 76 | |
| | LXM2-PL01-0080 | 80 | 86 | 80 | 155 | 70 | |
| | LXM2-PL01-0070 | 70 | 78 | 73 | 140 | 63 | |
| Amber | LXML-PL01-0060 | 60 | 61 | 60 | 98 | 39 | |
| | LXML-PL01-0050 | 50 | 54 | 51 | 84 | 33 | |
| | LXML-PL01-0040 | 40 | 48 | 46 | 77 | 30 | |
| | LXML-PL01-0030 | 30 | 38 | 37 | 61 | 24 | |

Notes for Table I:

1. Minimum luminous flux or radiometric power performance guaranteed within published operating conditions. Philips Lumileds maintains a tolerance of $\pm 6.5\%$ on flux and power measurements.
2. Typical luminous flux or radiometric power performance when device is operated within published operating conditions.

Flux Performance, Binning, and Supportability

LEDs are produced with semiconductor technology that is subject to process variation, yielding a range of flux performance that is approximately Gaussian in nature. In order to provide customers with fine granularity within the overall flux distribution, Philips Lumileds separates LEDs into fixed, easy to design with, minimum luminous flux bins. To verify supportability of parts chosen for your application design, please consult your Philips Lumileds sales representative.



Optical Characteristics

LUXEON Rebel Color Portfolio at Test Current ^[1] Thermal Pad Temperature = 25°C

Table 2.

| Color | Dominant Wavelength ^[2] λ_D , or Peak Wavelength ^[3] λ_P | | | Typical Spectral Half-width ^[4] (nm) $\Delta\lambda_{1/2}$ | Typical Temperature Coefficient of Dominant or Peak Wavelength (nm/°C) $\Delta\lambda_D / \Delta T_J$ | Typical Total Included Angle ^[5] (degrees) $\theta_{0.90V}$ | Typical Viewing Angle ^[6] (degrees) $2\theta_{1/2}$ |
|-------------------------------|---|----------|----------|---|---|---|--|
| | Min. | Typ. | Max. | | | | |
| Green ^[7] | 520.0 nm | 530.0 nm | 540.0 nm | 30 | 0.05 | 160 | 125 |
| Cyan ^[7] | 490.0 nm | 505.0 nm | 515.0 nm | 30 | 0.04 | 160 | 125 |
| Blue ^[7] | 460.0 nm | 470.0 nm | 485.0 nm | 20 | 0.05 | 160 | 125 |
| Royal-Blue ^{[3] [7]} | 440.0 nm | 447.5 nm | 460.0 nm | 20 | 0.04 | 160 | 125 |
| Red ^[8] | 620.0 nm | 627.0 nm | 645.0 nm | 20 | 0.05 | 160 | 125 |
| Deep Red ^[3, 8] | 650.0 nm | 655.0 nm | 670.0 nm | 20 | 0.05 | 160 | 125 |
| Red-Orange ^[8] | 610.0 nm | 617.0 nm | 620.0 nm | 20 | 0.08 | 160 | 125 |
| Amber ^[8] | 584.5 nm | 590.0 nm | 594.5 nm | 20 | 0.10 | 160 | 125 |
| PC Amber ^[7] | 587.8 nm | 591.0 nm | 592.0 nm | 80 | 0.10 | 160 | 120 |

Notes for Table 2:

1. LXML-PR01-XXXX, LXM2-PL01-XXXX and LXM3-PD01-XXXX emitters are tested at 350 mA, LXML-PR02-XXXX emitters are tested at 700 mA.
2. Dominant wavelength is derived from the CIE 1931 Chromaticity diagram and represents the perceived color. Philips Lumileds maintains a tolerance of ± 0.5 nm for dominant wavelength measurements.
3. Royal-blue and Deep Red LEDs are binned by radiometric power and peak wavelength rather than photometric lumens. Philips Lumileds maintains a tolerance of ± 2 nm for peak wavelength measurements.
4. Spectral width at $\frac{1}{2}$ of the peak intensity.
5. Total angle at which 90% of total luminous flux is captured.
6. Viewing angle is the off axis angle from lamp centerline where the luminous intensity is $\frac{1}{2}$ of the peak value.
7. PC amber, green, cyan, blue and royal-blue products are built with Indium Gallium Nitride (InGaN).
8. All red, deep red, red-orange, and amber are built with Aluminum Indium Gallium Phosphide (AlInGaP).

Electrical Characteristics

Electrical Characteristics at 350 mA for LUXEON Rebel color, Thermal Pad Temperature = 25°C

Table 3.

| Color | Part Number | Forward Voltage V_f [1] (V) | | | Typical Temperature Coefficient of Forward Voltage [2] (mV/°C) $\Delta V_f / \Delta T_j$ | Typical Thermal Resistance Junction to Thermal Pad (°C/W) $R\theta_{j-c}$ |
|------------|-------------|----------------------------------|------|------|---|--|
| | | Min. | Typ. | Max. | | |
| Green | LXML-PM01 | 2.55 | 2.90 | 3.51 | - 2.0 to - 4.0 | 10 |
| Cyan | LXML-PE01 | 2.55 | 2.90 | 3.51 | - 2.0 to - 4.0 | 10 |
| Blue | LXML-PB01 | 2.55 | 2.95 | 3.51 | - 2.0 to - 4.0 | 10 |
| Royal-Blue | LXML-PR01 | 2.55 | 2.95 | 3.51 | - 2.0 to - 4.0 | 10 |
| Red | LXML-PD01 | 2.31 | 2.90 | 3.51 | - 2.0 to - 4.0 | 12 |
| Red | LXM2-PD01 | 1.80 | 2.10 | 2.80 | - 2.0 to - 4.0 | 8 |
| Deep Red | LXM3-PD01 | 1.80 | 2.10 | 2.80 | - 2.0 to - 4.0 | 8 |
| Red-Orange | LXML-PH01 | 2.31 | 2.90 | 3.51 | - 2.0 to - 4.0 | 12 |
| Red-Orange | LXM2-PH01 | 1.80 | 2.10 | 2.80 | - 2.0 to - 4.0 | 8 |
| PC Amber | LXM2-PL01 | 2.55 | 3.05 | 3.51 | - 2.0 to - 4.0 | 10 |
| Amber | LXML-PL01 | 2.31 | 2.90 | 3.51 | - 2.0 to - 4.0 | 12 |

Electrical Characteristics at 700 mA for LUXEON Rebel ES Color, Thermal Pad Temperature = 25°C

| | | | | | | |
|------------|-----------|------|------|------|----------------|---|
| Royal-Blue | LXML-PR02 | 2.50 | 3.00 | 3.50 | - 2.0 to - 4.0 | 6 |
| Blue | LXML-PB02 | 2.50 | 2.95 | 3.50 | -2.0 to -4.0 | |

Notes for Table 3:

1. LUXEON Rebel ES colors measured between 25°C = T_j = 110°C and I_f = 700 mA.
2. Measured between 25°C = T_j = 110°C at I_f = 350 mA.
3. Philips Lumileds maintains a tolerance of ±0.06V on forward voltage measurements.

Typical Electrical Characteristics at 700 mA for LUXEON Rebel color, Thermal Pad Temperature = 25°C

Table 4.

| Color | Part Number | Typical Forward Voltage V_f (V) |
|------------|-------------|-----------------------------------|
| Green | LXML-PM01 | 3.25 |
| Cyan | LXML-PE01 | 3.25 |
| Blue | LXML-PB02 | 2.95 |
| Blue | LXML-PB01 | 3.30 |
| Royal-Blue | LXML-PR02 | 3.00 |
| Royal-Blue | LXML-PR01 | 3.25 |
| Red | LXML-PD01 | 3.60 |
| Red | LXM2-PD01 | 2.30 |
| Deep Red | LXM3-PD01 | 2.40 |
| Red-Orange | LXML-PH01 | 3.60 |
| Red-Orange | LXM2-PH01 | 2.30 |
| PC Amber | LXM2-PL01 | 3.20 |
| Amber | LXML-PL01 | 3.60 |

Absolute Maximum Ratings

Table 5.

| Parameter | Green/Cyan/ Blue/Royal Blue | LUXEON Rebel ES Royal Blue/ES Blue | Red/Deep-Red Red-Orange/Amber | PC Amber |
|---|---|---------------------------------------|----------------------------------|------------------|
| DC Forward Current (mA) | 1000 | 1000 | 700 | 700 |
| Peak Pulsed Forward Current (mA) | 1000 | 1200 | 700 | 700 |
| Average Forward Current (mA) | 1000 | 1000 | 700 | 700 |
| ESD Sensitivity | < 8000V Human Body Model (HBM) Class 3A JESD22-A114-B | | | |
| LED Junction Temperature ^[1] | 150°C | 150°C | 135°C | 130°C |
| Operating Case Temperature at 350 mA | -40°C - 135°C | -40°C - 135°C | -40°C - 120°C | -40°C - 110°C |
| Storage Temperature | -40°C - 135°C | -40°C - 135°C | -40°C - 135°C | -40°C - 135°C |
| Soldering Temperature | JEDEC 020c 260°C | JEDEC 020c 260°C | JEDEC 020c 260°C | JEDEC 020c 260°C |
| Allowable Reflow Cycles | 3 | 3 | 3 | 3 |
| Reverse Voltage (Vr) | Autoclave Conditions 121°C at 2 ATM 100% Relative Humidity for 96 Hours Maximum LUXEON Rebel Color Portfolio LEDs are not designed to be driven in reverse bias. | | | |

Notes for Table 5:

1. Proper current derating must be observed to maintain junction temperature below the maximum.
2. The maximum rating for LUXEON Rebel ES Royal Blue is 1200 mA with peak pulsed forward current not to exceed 60 seconds.

JEDEC Moisture Sensitivity

Table 6.

| Level | Floor Life | | Soak Requirements | |
|-------|------------|--------------------|-------------------|------------------|
| | Time | Conditions | Standard | |
| | | | Time (hours) | Conditions |
| I | unlimited | ≤ 30°C / 85% RH | 168 + 5 / -0 | 85°C / 85% RH |

Reflow Soldering Characteristics




Table 7.

| Profile Feature | Lead Free Assembly |
|--|--------------------|
| Average Ramp-Up Rate ($T_{s_{max}}$ to T_p) | 3°C / second max |
| Preheat Temperature Min ($T_{s_{min}}$) | 150°C |
| Preheat Temperature Max ($T_{s_{max}}$) | 200°C |
| Preheat Time ($t_{s_{min}}$ to $t_{s_{max}}$) | 60 - 180 seconds |
| Temperature T_L (t_L) | 217°C |
| Time Maintained Above Temperature T_L (t_L) | 60 - 150 seconds |
| Peak / Classification Temperature (T_p) | 260°C |
| Time Within 5°C of Actual Peak Temperature (t_p) | 20 - 40 seconds |
| Ramp-Down Rate | 6°C / second max |
| Time 25°C to Peak Temperature | 8 minutes max |

Note for Table 7:

- All temperatures refer to the application Printed Circuit Board (PCB), measured on the surface adjacent to the package body.

Mechanical Dimensions: LUXEON Rebel Color Emitter




Figure 1. Package outline drawing.

Notes for Figure 1:

- To avoid damage, do not handle the device by the emitter lens.
- Drawings not to scale.
- All dimensions are in millimeters.
- The thermal pad is electrically isolated from the anode and cathode contact pads.

Mechanical Dimensions: LUXEON Rebel ES Color Emitter




Figure 2. Package outline drawing.

Notes for Figure 2:

- To avoid damage, do not handle the device by the emitter lens.
- Drawings not to scale.
- All dimensions are in millimeters.
- The thermal pad is electrically isolated from the anode and cathode contact pads.

Pad Configuration




Figure 3. Pad configuration.

Note for Figure 3:

- The thermal pad is electrically isolated from the anode and cathode contact pads.

Solder Pad Design




Figure 4. Solder pad layout.

Notes for Figure 4:

- The photograph shows the recommended LUXEON Rebel Color Portfolio layout on printed circuit board (PCB). This design easily achieves a thermal resistance of 7K/W.
- Application Brief AB32 provides extensive details for this layout. The .dwg files are available at www.philipslumileds.com and www.philipslumileds.cn.com.

Wavelength Characteristics

Green, Cyan, Blue, all Royal Blue, Red, Red-Orange and Amber at Test Current, Thermal Pad Temperature = 25°C




Figure 5. Relative intensity vs. wavelength.

PC Amber at Test Current, Thermal Pad Temperature = 25°C





Figure 6. Relative intensity vs. wavelength.

Typical Light Output Characteristics over Temperature

Cyan, Blue, Royal Blue and LUXEON Rebel ES Royal Blue at Test Current



*LXML-PR02 and LXML-PB02 values are based on 700 mA drive current.

Figure 7. Relative light output vs. thermal pad temperature for green, cyan, blue, royal blue, LUXEON Rebel ES Royal Blue and ES Blue.

Red, Deep Red, Red-Orange and Amber at Test Current




Figure 8. Relative light output vs. thermal pad temperature for red, deep red, red-orange and amber.

Typical Forward Current Characteristics

Green, Cyan, Blue, Royal Blue, LUXEON Rebel ES Royal Blue and ES Blue
Thermal Pad Temperature = 25°C




Figure 9. Forward current vs. forward voltage for green, blue, royal blue, LUXEON Rebel ES Royal Blue and ES Blue.

Red, Deep Red, Red-Orange, Amber and PC Amber
Thermal Pad Temperature = 25°C




Figure 10. Forward current vs. forward voltage for red, deep red, red-orange, amber, and PC amber.

Typical Relative Luminous Flux

Typical Relative Luminous Flux vs. Forward Current for LUXEON Rebel ES Royal Blue and ES Blue, Thermal Pad Temperature = 25°C




Figure 11. Relative luminous flux or radiometric power vs. forward current for LUXEON Rebel ES Colors at Thermal Pad = 25°C maintained.

Typical Relative Luminous Flux vs. Forward Current for Green, Cyan, Blue and Royal Blue, Thermal Pad Temperature = 25°C




Figure 12. Relative luminous flux or radiometric power vs. forward current for green, cyan, blue and royal blue at Thermal Pad = 25°C maintained.

Typical Relative Luminous Flux vs. Forward Current for Red, Deep Red, Red-Orange, Amber, Thermal Pad Temperature = 25°C




Figure 13. Relative luminous flux vs. forward current for red, deep red, red-orange and amber at Thermal Pad = 25°C maintained.

Typical Relative Luminous Flux, PC Amber Thermal Pad Temperature = 25°C




Figure 14. Relative luminous flux vs. forward current for PC amber LXM2-PL01 emitters.

Current Derating Curves

Current Derating Curve for 350 mA Drive Current for Green, Cyan, Blue and Royal Blue




Figure 15. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 150^{\circ}C$, green LXML-PM01, cyan LXML-PE01, blue LXML-PB01 & royal blue LXML-PR01 emitters.

Current Derating Curve for 350 mA Drive Current for Red, Red-Orange, Amber




Figure 16. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 135^{\circ}C$, red LXML-PD01, red-orange LXML-PH01 & amber LXML-PL01 emitters.

Current Derating Curve for 350 mA Drive Current for Red, Deep-Red and Red-Orange




Figure 17. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 135^{\circ}C$, red LXM2-PD01, deep red LXM3-PD01 & red-orange LXM2-PH01 emitters.

Current Derating Curve for 350 mA Drive Current for PC Amber




Figure 18. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 130^{\circ}C$, PC amber LXM2-PL01 emitters.

Current Derating Curves

Current Derating Curve for 700 mA Drive Current for Green, Cyan, Blue and Royal Blue




Figure 19. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 150^{\circ}\text{C}$, green LXML-PM01, cyan LXML-PE01, blue LXML-PB01 & royal blue LXML-PR01 emitters..

Current Derating Curve for 700 mA Drive Current for LUXEON Rebel ES Royal Blue and ES Blue.




Figure 20. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 150^{\circ}\text{C}$, royal blue LXML-PR02 emitters.

Current Derating Curve for 700 mA Drive Current for Red, Red-Orange, Amber




Figure 21. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 135^{\circ}\text{C}$, red LXML-PD01, red-orange LXML-PH01 & amber LXML-PL01 emitters.

Current Derating Curve for 700 mA Drive Current for Red, Deep Red and Red-Orange




Figure 22. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 135^{\circ}\text{C}$, red LXM2-PD01, deep red LXM3-PD01 & red-orange LXM2-PH01 emitters.

Current Derating Curves

Current Derating Curve for 700 mA Drive Current for PC Amber




Figure 23. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 130^{\circ}\text{C}$, PC amber LXM2-PL01 emitters.

Current Derating Curve for 1000 mA Drive Current for Green, Cyan, Blue and Royal Blue




Figure 24. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 150^{\circ}\text{C}$, green LXML-PM01, cyan LXML-PE01, blue LXML-PB01 & royal blue LXML-PR01.

Current Derating Curve for 1000 mA Drive Current for LUXEON Rebel ES Royal Blue and ES Blue




Figure 25. Maximum forward current vs. ambient temperature, based on $T_{JMAX} = 150^{\circ}\text{C}$, royal blue LXML-PR02 emitters.

Typical Radiation Patterns

Typical Spatial Radiation Pattern for Green, Cyan, Blue, Royal Blue, LUXEON Rebel ES Royal Blue and ES Blue Lambertian




Figure 26. Typical spatial radiation pattern for green, cyan, blue, royal blue, LUXEON Rebel ES Royal Blue and ES blue lambertian.

Typical Polar Radiation Pattern for Green, Cyan, Blue, Royal Blue, LUXEON Rebel ES Royal Blue and ES Blue Lambertian




Figure 27. Typical polar radiation pattern for green, cyan, blue, royal blue and LUXEON Rebel ES royal blue lambertian.

Typical Spatial Radiation Pattern for Red, Red-Orange and Amber Lambertian




Figure 28. Typical spatial radiation pattern for red, red-orange and amber lambertian.

Typical Polar Radiation Pattern for Red, Red-Orange and Amber Lambertian




Figure 29. Typical polar radiation pattern for red, red-orange and amber lambertian.

Typical Spatial Radiation Pattern for Deep Red Lambertian




Figure 30. Typical spatial radiation pattern for deep red lambertian.

Typical Polar Radiation Pattern for Deep Red Lambertian




Figure 31. Typical polar radiation pattern for deep red lambertian.

Typical Radiation Patterns

Typical Spatial Radiation Pattern PC Amber




Figure 32. Typical representative spatial radiation pattern, PC amber LXM2-PL01 emitters.

Typical Polar Radiation Pattern PC Amber




Figure 33. Typical polar radiation pattern, PC amber LXM2-PL01 emitters.

Typical Chromaticity Characteristics PC Amber

Typical Chromaticity Characteristics over Temperature




Figure 34. Chromaticity coordinate vs. thermal pad temperature. Test current: 350 mA.

Typical Chromaticity Characteristics over Forward Current Thermal Pad Temperature = 25 °C




Figure 35. Chromaticity coordinate vs. forward current.

Emitter Pocket Tape Packaging




Figure 36. Emitter pocket tape packaging.

Emitter Reel Packaging




Figure 37. Emitter reel packaging.

Product Binning and Labeling

Purpose of Product Binning

In the manufacturing of semiconductor products, there is a variation of performance around the average values given in the technical data sheets. For this reason, Philips Lumileds bins the LED components for luminous flux, color and forward voltage (V_f).

Decoding Product Bin Labeling

LUXEON Rebel Color Portfolio emitters are labeled using a three or four digit alphanumeric code (CAT code) depicting the bin values for emitters packaged on a single reel. All emitters packaged within a reel are of the same 3-variable bin combination. Using these codes, it is possible to determine optimum mixing and matching of products for consistency in a given application.

Format of Labeling for Emitters

Reels of green, cyan, blue, royal blue, red, red-orange, amber and PC amber emitters are labeled with a three digit alphanumeric CAT code following the format below.

ABC

A = Flux bin (J, K, L, M etc.)

B = Color bin (2, 4, 6 etc.)

C = V_f bin (D, E, F, G etc.)

Luminous Flux Bins

Tables 8, 9 and 10 list the standard photometric luminous flux/radiometric power bins for LUXEON Rebel and LUXEON Rebel ES color emitters (tested and binned at 350 mA and 700 mA respectively). Although several bins are outlined, product availability in a particular bin varies by production run and by product performance. Not all bins are available in all colors.

Table 8.

| Flux Bins All Colors (except Royal Blue and Deep Red) | | |
|---|-------------------|-------------------|
| Bin Code | Minimum Flux (lm) | Maximum Flux (lm) |
| D | 18.1 | 23.5 |
| E | 23.5 | 30 |
| F | 30 | 40 |
| G | 40 | 50 |
| H | 50 | 60 |
| J | 60 | 70 |
| K | 70 | 80 |
| L | 80 | 90 |
| M | 90 | 100 |
| N | 100 | 110 |
| X | 110 | 120 |
| P | 120 | 130 |
| Y | 130 | 140 |

Table 9.

| LUXEON Rebel Royal-Blue and LUXEON Rebel ES Royal Blue | | |
|--|-------------------------------|-------------------------------|
| Bin Code | Minimum Radiometric Flux (mW) | Maximum Radiometric Flux (mW) |
| D | 350 | 425 |
| E | 425 | 500 |
| F | 500 | 600 |
| G | 600 | 700 |
| H | 700 | 800 |
| J | 800 | 900 |
| K | 900 | 950 |
| Y | 950 | 1000 |
| A | 1000 | 1050 |
| B | 1050 | 1100 |
| M | 1100 | 1200 |

Table 10.

| LUXEON Rebel Deep Red | | |
|-----------------------|-------------------------------|-------------------------------|
| Bin Code | Minimum Radiometric Flux (mW) | Maximum Radiometric Flux (mW) |
| C | 260 | 300 |
| D | 300 | 350 |
| E | 350 | 400 |

Forward Voltage Bins

The following forward voltage bins include the minimum and maximum V_f bin values for the emitter. Although several bins are outlined, product availability in a particular bin varies by production run and by product performance.

Table 11. Applicable for LXML-PXXI and LXM2-PL01 (PC Amber) emitters.

| V_f Bins | | |
|------------|--------------------------------|--------------------------------|
| Bin Code | Minimum Forward Voltage (V) | Maximum Forward Voltage (V) |
| A | 2.31 | 2.55 |
| B | 2.55 | 2.79 |
| C | 2.79 | 3.03 |
| D | 3.03 | 3.27 |
| E | 3.27 | 3.51 |

Table 12. Applicable for LXML-PR02-XXXX (ES Royal Blue) and LXML-PB02-XXXX (ES Blue) emitters tested at 700 mA.

| Bin Code | Minimum Forward Voltage (V) | Maximum Forward Voltage (V) |
|----------|--------------------------------|--------------------------------|
| P | 2.50 | 2.75 |
| R | 2.75 | 3.00 |
| S | 3.00 | 3.25 |
| T | 3.25 | 3.50 |

Table 13. Applicable for LXM2-PXXI (Red and Red Orange) and LXM3-PD01 (Deep Red) emitters tested at 350 mA.

| Bin Code | Minimum Forward Voltage (V) | Maximum Forward Voltage (V) |
|----------|--------------------------------|--------------------------------|
| V | 1.80 | 2.00 |
| W | 2.00 | 2.20 |
| X | 2.20 | 2.40 |
| Y | 2.40 | 2.60 |
| Z | 2.60 | 2.80 |

Color Bins

Green, cyan and blue LUXEON Rebel color emitters are tested and binned for dominant wavelength.

Dominant Wavelength Bin Structure for Green Emitters

Table 14.

| Bin Code | Minimum Dominant Wavelength (nm) | Maximum Dominant Wavelength (nm) |
|----------|-------------------------------------|-------------------------------------|
| 1 | 520 | 525 |
| 2 | 525 | 530 |
| 3 | 530 | 535 |
| 4 | 535 | 540 |

Dominant Wavelength Bin Structure for Cyan Emitters

Table 15.

| Bin Code | Minimum Dominant Wavelength (nm) | Maximum Dominant Wavelength (nm) |
|----------|-------------------------------------|-------------------------------------|
| 1 | 490 | 495 |
| 2 | 495 | 500 |
| 3 | 500 | 505 |
| 4 | 505 | 510 |
| 5 | 510 | 515 |

Dominant Wavelength Bin Structure for Blue and LUXEON Rebel ES Blue Emitters

Table 16.

| Bin Code | Minimum Dominant Wavelength (nm) | Maximum Dominant Wavelength (nm) |
|----------|-------------------------------------|-------------------------------------|
| 1 | 460 | 465 |
| 2 | 465 | 470 |
| 3 | 470 | 475 |
| 4 | 475 | 480 |
| 5 | 480 | 485 |

Royal blue LUXEON Rebel and LUXEON Rebel ES emitters are tested and binned for peak wavelength.

Peak Wavelength Bin Structure for Royal Blue and LUXEON Rebel ES Royal Blue Emitters

Table 17.

| Bin Code | Minimum Peak Wavelength (nm) | Maximum Peak Wavelength (nm) |
|----------|---------------------------------|---------------------------------|
| 3 | 440 | 445 |
| 4 | 445 | 450 |
| 5 | 450 | 455 |
| 6 | 455 | 460 |

Red, red-orange and amber LUXEON Rebel color emitters are tested and binned for dominant wavelength.

Dominant Wavelength Bin Structure for Red Emitters

Table 18.

| Bin Code | Minimum Dominant Wavelength (nm) | Maximum Dominant Wavelength (nm) |
|----------|-------------------------------------|-------------------------------------|
| 4 | 620.0 | 630.0 |
| 5 | 630.0 | 645.0 |

Dominant Wavelength Bin Structure for Red-Orange Emitters

Table 19.

| Bin Code | Minimum Dominant Wavelength (nm) | Maximum Dominant Wavelength (nm) |
|----------|-------------------------------------|-------------------------------------|
| 2 | 610.0 | 620.0 |

Dominant Wavelength Bin Structure for Amber Emitters

Table 20.

| Bin Code | Minimum Dominant Wavelength (nm) | Maximum Dominant Wavelength (nm) |
|----------|-------------------------------------|-------------------------------------|
| 1 | 584.5 | 587.0 |
| 2 | 587.0 | 589.5 |
| 4 | 589.5 | 592.0 |
| 6 | 592.0 | 594.5 |

Peak Wavelength Bin Structure for Deep Red Emitters

Table 21.

| Bin Code | Minimum Dominant Wavelength (nm) | Maximum Dominant Wavelength (nm) |
|----------|-------------------------------------|-------------------------------------|
| 6 | 650 | 660 |
| 7 | 660 | 670 |

Table 22.

| PC Amber Bin Coordinates | | |
|--------------------------|--------|--------|
| Bin Code | x | y |
| 2 | 0.5622 | 0.4372 |
| | 0.5576 | 0.4326 |
| | 0.5775 | 0.4132 |
| | 0.5843 | 0.4151 |

Note for Table 22:

- LUXEON Rebel PC amber emitters are tested and binned by x,y coordinates.

Color Bins PC Amber




Figure 38. Color bin structure.

Company Information

Philips Lumileds is a leading provider of LEDs for everyday lighting applications. The company's records for light output, efficacy and thermal management are direct results of the ongoing commitment to advancing solid-state lighting technology and enabling lighting solutions that are more environmentally friendly, help reduce CO₂ emissions and reduce the need for power plant expansion. Philips Lumileds LUXEON® LEDs are enabling never before possible applications in outdoor lighting, shop lighting, home lighting, consumer electronics, and automotive lighting.

Philips Lumileds is a fully integrated supplier, producing core LED material in all three base colors, (Red, Green, Blue) and white. Philips Lumileds has R&D centers in San Jose, California and in the Netherlands, and production capabilities in San Jose, Singapore and Penang, Malaysia. Founded in 1999, Philips Lumileds is the high flux LED technology leader and is dedicated to bridging the gap between solid-state technology and the lighting world. More information about the company's LUXEON LED products and solid-state lighting technologies can be found at www.philipslumileds.com.

©2013 Philips Lumileds Lighting Company. All rights reserved.
Product specifications are subject to change without notice.

PHILIPS
LUMILEDS

www.philipslumileds.com
www.philipslumileds.cn.com