




# Blind Threaded Inserts




ELOO Avdel® iForm™

Since 1922 Since 1936

2010





## Easily adaptable for your materials and production processes

Everywhere that you need to join components reliably and efficiently Avdel® offers intelligent fastening systems and the most suitable installation tools and assembly stations.

Wherever you need high quality, load bearing threads in thin materials, the Avdel® Blind Threaded Insert System offers the ideal solution.

Quickly and reliably installed without rework or damage to the parent application, even with painted sheet materials and tubes where there is no blind side access.

Avdel® threaded inserts are most commonly used in the automotive, vehicle, electronics chassis manufacturing, equipment manufacturing and shipbuilding industries.


The wide variety of Avdel® threaded inserts provides perfect engineering results and economic solutions in every application.

Together with our customers we develop blind fastening systems that simplify your production processes and improve the quality of your products. We see ourselves not only as a provider of fasteners, tools and assembly systems, but also as a system and development partner with the objective of helping our customers improve their assembly performance.

# Contents Page

---

Overview	Avdel® Threaded Inserts	4
	Benefits of Assembly	5
	Design Features and Benefits	6
	Customised Designs	7
	Selecting a Threaded Insert	8
	Design Parameters	9
	Selection Guide	10
The Range of Avdel® Threaded Inserts	Eurosert®	11
	Nutsert®/TSN®	12
	DK/DL	13
	Hexsert®/Euro Hexsert®	14
	High Strength Hexsert®	15
	Squaresert®	16
	Versa-Nut®	17
Installation Equipment	Installation Tools	19
	Handtools	20-21
	Automated Assembly Systems	22
	Assembly Applications	23
	Assembly Workstations	24
Data Sheets	Eurosert®	26-28
	Nutsert®/TSN®	29-37
	DK/DL	38-41
	Hexsert®/Euro Hexsert®	42-46
	High Strength Hexsert®	47
	Squaresert®	48
	Versa-Nut®	49
The Range of Avdel® Blind Fastening Systems		51



# Avdel® Threaded Inserts

Avdel® threaded inserts and installation tools provide a quick, reliable and low cost system of inserting high quality, load bearing threads in thin gauge materials. Avdel® threaded inserts offer many benefits over nuts and bolts, weld nuts, self-tapping screws and pressed inserts.

## Benefits of Assembly

### Blind sided assembly

Access is needed to only one side of the workpiece. This results in increased speed of assembly, lower assembly costs, reduced operator error and is ideal for assembly of box or closed sections.

### Purely mechanical fastening

Avdel® threaded inserts can be used to join dissimilar materials. They avoid damage of surface coatings and thus can be installed in pre- as well as in post finished applications. The workpiece is not affected by a welding process.

### Designed for rapid rate of installation

The typical assembly cycle of 3 seconds reduces assembly time and costs.

### Designed for automation

Avdel® threaded inserts can be installed fully automatically resulting in a high speed and precision assembly. The set up costs are lower compared to welding equipment.

### Forms a permanent fixture in material


Avdel® threaded inserts deliver a vibration resistant joint without requiring maintenance.

### Multi-functional fastener

Threaded inserts feature multi functions: they provide a female thread in sheet while giving the opportunity to clamp two or more sheets at the same time; can act as a spacer - resulting in fewer components required.

### Suitable for a wide range of installation tools

The facilities of installation range from hand tools for small batch and repair work and pneumatic tools for medium volume up to full automation for in-line assembly.



# Benefits of Assembly

## Automotive

- Clamps securely into parent material giving high resistance to vibration and attendant loosening of joint
- Ideal for joining dissimilar materials (e.g. aluminium to plastic sections) in addition to providing a female thread
- Particularly suitable for installing threads into closed sections where there is no access to blind side
- Available in high corrosion resistant coatings such as zinc-nickel to conform to increasing corrosion warranty periods
- Lower cost and less hazardous alternative to weld nuts, with far less damage to parent material
- Can easily be installed after paint finish is applied to avoid clogging threads, unlike weld nuts
- Quick and flexible placement possible in confined areas using hand tools
- Will not deform, distort or damage parent material, even if this is painted prior to installation
- Colour of insert can be modified to match parent material or improve appearance of assembly

## Electronic and Electrical Equipment

- Closed end inserts prevent ingress of water and foreign bodies into electrical circuits
- No risk of nuts coming loose or falling on to circuitry
- Inserts can act as an earthing point
- Forms permanent fixing in parent material allowing easier panel removal and replacement compared to nut and bolt fixings
- Multi-functionality of thread, rivet and flange-spacer combined, offers space and weight advantages over other attachment methods



Speaker systems

## Process Automation

- Ease of hole entry afforded by the reduced tail end diameter of Avdel inserts improves suitability for automatic placing
- Autosert® machines can place up to 20 inserts per minute using a single placing head
- Automation improves control of placing, removing risk of operator error
- Ideal for labour intensive and highly repetitive placing sequences
- Autosert® machines are capable of inserting several inserts simultaneously offering a significant reduction in process time



4 Autosert® automated assembly systems

# Design Features and Benefits

Design Feature	Design Benefits	Typical Applications
Splined Body	 <ul style="list-style-type: none"> <li>Improves torque-to-turn resistance in softer materials such as aluminium when compared to plain body inserts</li> <li>Improved electrical continuity in sheet metal fixings</li> </ul>	<ul style="list-style-type: none"> <li>Soft materials such as aluminium, magnesium, plastics, composites and wood</li> <li>Earthing points in electrical assemblies</li> </ul>
Hexagonal Body	 <ul style="list-style-type: none"> <li>Hexagonal section and bore improves torque-to-turn in components via form lock when compared to round and splined inserts</li> </ul>	<ul style="list-style-type: none"> <li>Automotive chassis components requiring high resistance to turning under vibrating loads</li> <li>Where high bolt removal torque is required during servicing (e.g. switchgear cabinets)</li> <li>Thermal applications prone to high expansion and contraction in parent material</li> </ul>
Square Body	 <ul style="list-style-type: none"> <li>Square section and bore improves torque-to-turn in components via form lock due to even greater contact surface compared to round and splined inserts</li> <li>Increased hole punch life compared to hexagonal geometries</li> </ul>	<ul style="list-style-type: none"> <li>Automotive body mountings requiring maximum turning resistance</li> <li>Soft material constructions, particularly for plastics, composites and soft sheet metals</li> </ul>
Large Flange	 <ul style="list-style-type: none"> <li>Provides large load bearing surface</li> <li>Reinforces hole, preventing push through</li> <li>Potential to use flange as a spacer</li> <li>Can be used with underhead seal (e.g. Rimlex®)</li> </ul>	<ul style="list-style-type: none"> <li>Load bearing applications in thin sheet and soft material applications</li> <li>Mountings where high push-out resistance is required (e.g. adjustable foot mountings)</li> </ul>
Low Profile	 <ul style="list-style-type: none"> <li>Near flush installation and clamp up</li> </ul>	<ul style="list-style-type: none"> <li>Flush fitting, thin sheet, low load bearing applications (e.g. domestic appliances and coach building)</li> </ul>
Countersunk	 <ul style="list-style-type: none"> <li>Flush installation and secure clamp up</li> </ul>	<ul style="list-style-type: none"> <li>Flush fitting, thin sheet, low load bearing applications (e.g. domestic appliances and coach building)</li> </ul>
Closed End	 <ul style="list-style-type: none"> <li>Prevents ingress of dirt and fluids into thread</li> <li>Prevents ingress of water and foreign bodies into electrical circuits</li> </ul>	<ul style="list-style-type: none"> <li>Electrical assemblies to prevent foreign bodies being inserted through open thread</li> <li>Load bearing sections to avoid thread exposure</li> <li>With underhead seal (Rimlex®) to prevent ingress of fluids and dirt into protected environment (e.g. fuel tank)</li> </ul>
Reduced Tail End Diameter	 <ul style="list-style-type: none"> <li>Ease of hole entry</li> <li>Particularly suited for automation</li> </ul>	<ul style="list-style-type: none"> <li>Automated feed systems</li> <li>Rapid manual assembly</li> </ul>
Increased Thread Strength	 <ul style="list-style-type: none"> <li>Improves the maximum torque capability by typically 100% compared to standard Hexsert®</li> <li>No risk of thread-stripping insert, avoiding expensive and time consuming re-work</li> <li>Potential to downsize insert and screw diameter for a given joint clamp load</li> </ul>	<ul style="list-style-type: none"> <li>Structural automotive fixings into closed aluminium extrusions and hydro-formed steel tubes</li> <li>High strength threads into thin, hardened steel pressings unsuited to welding</li> <li>Any application where routine screw removal and re-tightening without torque control is likely</li> </ul>
Slotted Body	 <ul style="list-style-type: none"> <li>Forms four folded legs providing an extra large blind side bearing area</li> </ul>	<ul style="list-style-type: none"> <li>Use with composites and plastics, reducing risk of cracking around the hole</li> </ul>

# Customised Designs

## Modified Feature

Flange Diameter



## Typical Uses and Benefits

- Greater diameter increases push-out force and hole reinforcement in soft and thin gauge metals

Flange Thickness



- Thicker flange acts as a spacer and provides a slight increase in push-out force

Nut Length



- Greater length acts as a blind side spacer and increases thread strength

Body Diameter



- Greater body diameter increases thread strength, torque-to-turn and push-out force
- Particularly suitable where the designer wishes to retain a large hole size for a small thread

Grip Range



- Increase in grip is required to accommodate thick wall constructions such as those using aluminium, magnesium, plastics and composites

Special Cold Formed Products



- In high volumes, these can offer significant cost savings compared to equivalent machined components
- Designs possible to very high tolerances for use with your own tooling

Coatings



- Special finishes can improve corrosion resistance, appearance and colour match with parent materials

Surface Hardening



- Treatments such as nitriding increase thread torque strength

Closed Ends and Underhead Seals



- Provides maximum protection against the ingress of moisture and dirt

Thread Forms



- We can offer a wide range of metric and imperial thread forms to suit your application, including UNC, UNF, BSW, BSF, BA and fine series metric threads

# Selecting a Threaded Insert

Selecting a threaded insert is a simple process. The six factors detailed below are designed to help you identify an insert suitable for your application:

## Thread size

Avdel® threaded inserts range from M3 to M12 thread sizes dependent upon the insert. Imperial threads are also available – please refer to page 10.

## Grip range

The threaded insert should be selected to ensure that the thicknesses of the parent material(s) falls within the grip range.

## Hole size

This is specified on the relevant technical data page for the insert. Allowance for coating the parent material should be made to avoid an undersized hole.

## Torque-to-turn

Resistance is dependent upon the body shape and increases in the series: round, splined, hexagonal and square. Please refer to page 9 for further information.

## Special features


Additional features such as low profile, large flange, closed end and countersunk are available within the standard range of products. Please refer to page 7 for details on special features and finishes.

## Corrosion resistance




The selection of the material type and coating of the threaded insert should be made on the basis of the corrosion resistance required.

## Important Information

The information on this page should be used in conjunction with the technical data available on our website [www.avdel-global.com](http://www.avdel-global.com) where you can also find additional information about corrosion, safety and RoHS.



# Design Parameters



The above table is based on data derived from Salt Spray tests in accordance with ASTM B 117 using 5% sodium chloride fog. The ranking of surface finishes shown in the above table has been obtained from these tests. These are carried out under standard conditions using sodium chloride solution fog as a means of comparing the potential corrosion resistance. The conditions in all other applications are often different and could affect the comparative ranking. In particular, if dissimilar metals are involved the subsequent galvanic action can influence the rate and nature of corrosion.

The ranking shown is based on the time of appearance of red rust but the same overall pattern is true for time of onset of white rust. Salt Spray tests are less applicable to stainless steel, but its inclusion in the table serves to illustrate its increased inherent corrosion resistance. We would be happy to discuss the requirements for your particular application and to assist you in selecting the most appropriate finish.

# Selection Guide

This table is designed as a guide to help you select the most suitable Avdel® threaded insert for your particular application. Full technical and performance data for each threaded insert can be found on our website or contact your local Avdel representative.

Product Range	Body Shape	Material	Design Features	Hole Sizes	Thread Size		Page No.
Eurosert®	●	Aluminium Steel	Closed End Open End Large Flange Low Profile Countersunk	Metric Imperial	M3 M4 M5 M6 M8 M10 M12	These data sheets will be available on our website <a href="http://www.avdel-global.com">www.avdel-global.com</a>	
Nutsert® / TSN®	●						9408
	●						39002
	●						39006
							9468
							9658
							FS38
							FS58
							FW78
							FW96
							GM17
							GM57
							GM68
							9654
							9655
							9665
DK/DL	●					DKA	38
	●					DKS	39
	●					DLA	40
	●					DLS	41
Hexsert® / Euro Hexsert®	●					9498	42
	●					9688	43
	●					39101	14 44
	●					39102	45
	●					49141	46
High Strength Hexsert®	●					39301	15 47
Squaresert®	■					GK08	16 48
Versa-Nut®	●					VN21	17 49

\*These data sheets will be available on our website [www.avdel-global.com](http://www.avdel-global.com)

Our policy is one of continuous product development and improvement and we reserve the right to change the specification of any product without prior notice.



Steel inserts designed to provide load bearing threads in thin sheet materials. For hard metric hole sizes.



## Key features and benefits

- Can be used in very thin sheet materials from 0.25mm (0.01")
- Double diameter body and lead-in chamfer provide easy insertion into hole
- Various platings available to increase corrosion resistance
- Splined body improves torque-to-turn resistance in softer materials such as aluminium when compared to plain body inserts and improves electrical continuity in sheet metal fixings
- Low profile head allows near flush fit to application
- Large flange head provides a load bearing surface and reinforces the hole to prevent push-out. Can be used as a spacer and can be supplied with an underhead seal.
- Can be used with hand tools, pneumatic tools and fully automated machines to suit a wide range of assembly methods

## Specifications

Thread Sizes:

M3 – M10

Material:

Steel

Headforms:

Low profile and large flange


Body:

Round, with or without splines

Hole Size:

Metric

## Typical placing sequence



Please visit our website [www.avdel-global.com](http://www.avdel-global.com) for fastener placing animations and technical data.

## Assembly applications

- Automotive
- Electrical engineering
- Electronic components
- Sheet metal
- Domestic appliances
- General light fabrication



# Nutsert®/TSN®



Steel, stainless steel or aluminium inserts designed to provide load bearing threads in thin sheet materials.



## Key features and benefits

- Can be used in very thin sheet materials from 0.50mm (0.02")
- Various platings available to increase the corrosion resistance
- Low profile head allows near flush fit to application
- Large flange head provides a load bearing surface and reinforces the hole to prevent push-out. Can be used as a spacer and can be supplied with an under-head seal
- Closed end prevents the ingress of dirt and fluids into thread and electrical circuits
- Can be used with hand tools, pneumatic tools and fully automated machines to suit a wide range of assembly methods

## Specifications

### Thread Sizes:

M3 – M10, 6-32 UNC,  
8-32 UNC, 10-24 UNC,  
1/4-20 UNC, 5/16-18 UNC,  
3/8-16 UNC

### Materials:

Steel, stainless steel,  
aluminium

### Headforms:

Low profile and large flange


### Option:

Closed end

### Hole Size:

Mainly imperial. Soft metric  
for large flange options


## Typical placing sequence



Please visit our website [www.avdel-global.com](http://www.avdel-global.com) for fastener placing animations and technical data.

## Assembly applications

- Automotive
- Electrical engineering
- Electronic components
- Sheet metal
- Domestic appliances
- General light fabrication



# DK/DL



Steel or aluminium inserts designed to provide load bearing threads in thin sheet materials.



## Key features and benefits

- Can be used in very thin sheet materials from 0.50mm (0.02")
- Wide grip range provides a placing capability in material thickness ranging from 0.5 mm (.02") up to 7.9 mm (.312")
- Splined body provides increased torque-to-turn resistance over conventional non-splined inserts
- Low profile head allows near flush seating without special hole preparation
- Large flange version provides a large bearing surface which increases push-out performance
- Reduced tail end diameter offers ease of hole entry

## Specifications

### Thread Sizes:

M4 - M10, 6-32 UNC,  
8-32 UNC, 10-24 UNC,  
10-32 UNF, 1/4-20 UNC,  
1/4-28 UNF, 5/16-18 UNC,  
5/16-24 UNF, 3/8-16 UNC,  
3/8-24 UNF

### Materials:

Steel, aluminium

### Headforms:

Low profile and large flange


### Body:

Splined

### Hole Size:

Imperial

## Typical placing sequence



Please visit our website [www.avdel-global.com](http://www.avdel-global.com) for fastener placing animations and technical data.

## Assembly applications

- Automotive
- Electrical engineering
- Sheet metal
- Domestic appliances
- General light fabrication



# Hexsert® and Euro Hexsert®



Inserts with hexagonal body, providing high torque-to-turn and pull-out performance, particularly in soft metals.



## Key features and benefits

- Hexagonal section and bore improves torque-to-turn in components via form lock when compared to round and splined inserts
- Superior pull-out performance
- Can be used for very thin sheet materials from 0.50 mm (0.02")
- Double diameter body and lead-in chamfer provide easy insertion into hole
- Access needed from only one side of the application, for high speed assembly
- Various platings available to increase corrosion resistance
- Low profile head allows near flush fit to application
- Large flange head provides a load bearing surface and reinforces the hole to prevent push-out. Can be used as a spacer and can be supplied with an underhead seal.
- Closed end prevents the ingress of dirt and fluids into thread and electrical circuits
- Can be used with hand tools, pneumatic tools and fully automated machines to suit a wide range of assembly methods

## Specifications

Thread Sizes:

M3 – M12

Materials:

Steel, stainless steel

Headforms:

Low profile and large flange

Body:

Hexagonal


Option:

Closed end

Hole Size:

Metric and imperial options


## Typical placing sequence



Please visit our website [www.avdel-global.com](http://www.avdel-global.com) for fastener placing animations and technical data.

## Assembly applications

- Automotive chassis components
- Electrical engineering
- Sheet metal
- Domestic appliances
- Switchgear cabinets
- Thermal applications



# High Strength Hexsert®



High strength Hexsert® provides clamp force comparable to weld nuts and clinch nuts in high torque applications. They offer equivalent thread proof load strength to ISO 898 Property Class 10 weld nuts and clinch nuts, and can handle tightening torques commonly applied to Property Class 10.9 and 12.9 screws and bolts.



## Key features and benefits

- Exceptional torque capability
- High speed assembly
- Provides high-strength threads in thin materials starting at 0.5mm
- Increased thread strength
- If excessive torque is applied, the screw shank should fail before the insert, avoiding over-tightening problems such as thread stripping and expensive rework
- Installed with standard Avdel handtools, as well as multi-head and auto-feed robotic systems

## Specifications

Thread Sizes:

M6 – M12

Material:

Steel

Headforms:

Large flange

Body:


Hexagonal

Hole Size:

Metric

Avdel Patent Protected.

## Typical placing sequence



Please visit our website [www.avdel-global.com](http://www.avdel-global.com) for fastener placing animations and technical data.

## Assembly applications

- Tubular steel
- Hydroformed parts
- Magnesium castings
- Aluminum extrusions



# Squaresert®



Steel inserts with square body, providing very high torque-to-turn and pull-out performance in all materials.



## Key features and benefits

- Square section and bore improves torque-to-turn in components via form lock due to even greater contact surface compared to round and splined inserts
- Increases hole punch life compared to hexagonal geometries
- Superior pull-out performance
- Can be used for very thin sheet materials from 0.50mm (0.02")
- Various platings available to increase corrosion resistance
- Large flange head provides a load bearing surface and reinforces the hole to prevent push-out
- Can be used as a spacer and can be supplied with an underhead seal
- Can be used with hand tools, pneumatic tools and fully automated machines to suit a wide range of assembly methods

## Specifications

Thread Sizes:

M5 – M8

Material:

Steel


Headform:

Large flange

Hole Size:

Metric

## Typical placing sequence



Please visit our website [www.avdel-global.com](http://www.avdel-global.com) for fastener placing animations and technical data.

## Assembly applications

- Automotive body mountings
- Electrical enclosures
- Soft sheet metal
- Plastics & composites
- Domestic appliances
- General light fabrication



# Versa-Nut®



Versa-Nut® inserts are designed for blind-sided use in soft materials, plastics and composites. Versa-Nut® Inserts have a higher pull out and torque-to-turn resistance than most alternative blind inserts. The insert's higher strength allows designers to reduce the size or number of fasteners in an assembly and because it features a grip range far greater than that of a standard rivet nut, it suits a wide number of applications.



## Key features and benefits

- Specially designed for use in soft or weak materials, plastics, composites, or very thin panels
- Large head size spreads clamp load of assembled joint
- Additional benefits against conventional inserts:
  - 1) Extra large blind side bearing area after placing offers:
    - Higher pull-out and torque-to-turn resistance
    - Less radial loading of holes in brittle materials
    - Less risk of cracking and de-lamination of composites
  - 2) Up to twice the grip range of standard blind inserts:
    - Enables a designer to reduce the size or number of fasteners in an assembly
    - Covers large variations of thicknesses

## Specifications

Thread Sizes:

M4 – M8

Material:

Steel

Headform:

Large flange


Body:

Round

Hole Size:

Imperial

## Typical placing sequence




Please visit our website [www.avdel-global.com](http://www.avdel-global.com) for fastener placing animations and technical data.

## Assembly applications

- Blow-molded automotive parts and trim fixings
- Sandwiched sections, and composite panels in truck, bus, caravan and marine interiors
- General composite and plastic sections for toys
- Small domestic appliances
- Containers
- Display panels
- Plastic furniture
- Fiberboard and plywood assemblies





# Installation Tools

Avdel offers a highly cost effective and flexible range of hand operated power tools for placing threaded inserts. The range is designed to meet the needs of different applications and assembly environments as well as different types of threaded inserts. Key benefits include:


- Lower in-place costs through high speed, accurate placement of inserts
- Greater production flexibility from batch work to assembly line
- Improved product quality through reliable and secure thread installation
- Maximum operator comfort and improved ergonomics

## Handtools

Avdel Threaded Insert Power Tools use the ‘spin-pull’ technology:

### The benefits of ‘spin-pull’ technology

- Generates high pull forces required to place large diameter and thick wall inserts
- Reduces wear on the drive screw resulting in lower maintenance and longer tool lifetime
- Compact, ergonomically designed tools which can be suspended or hand held
- Allows placement of lubricated and unlubricated inserts



# Handtools

## 74200 model

A high performance hydro-pneumatic power tool in heavy duty plastic, designed for rapid, blind sided installation of threaded inserts from M3 to M12.

- Heavy duty plastic tool body and long-life components provide a durable and robust construction for a long working life. Ideal for demanding production environments
- The ergonomic design provides for reduced operator fatigue and increased productivity. The tool can be suspended or hand held
- Latest 'spin-pull' technology ensures accurate and secure thread installation and reduces wear on the drive screw.
- Places lubricated and unlubricated inserts
- Lightweight design makes it portable and easy to handle
- Average cycle time of 2.5 secs reduces assembly time to a minimum

## 74201 model

The 74201 tool complements the 74200 model by offering the additional feature of pressure setting so that the insert is always fully formed, regardless of clamping capacity changes. It is designed for applications where inserts are being placed into the same application with varying sheet thicknesses, which is increasingly the case with the use of plastics, composite materials and magnesium and aluminium castings. The 74201 is also advantageous in conditions where swarf may be present at the back of drilled holes and for blind holes (i.e. tubes) where you cannot see if the insert has correctly formed - body building, instrument panel beams.

The tool installs inserts to a set hydraulic pressure (which may be adjusted), rather than operating to a fixed stroke. This eliminates the need to adjust stroke or to use more than one tool to install inserts into different thicknesses, improving product quality and reducing assembly cycle times.

- The pressure setting allows operators to install same fastener into varying material thickness without any adjustment to stroke. Thus eliminates operator responsibility for setting tool stroke and also overcomes rear sheet swarf issues
- Utilises standard 74200 nose equipment and can install M3 to M8 inserts
- The ergonomic design provides for reduced operator fatigue and increased productivity. The tool can be suspended or hand held
- The plastic covered cast and aluminium body provides highly impact resistance when dropped. The tool does not rely on plastic casing to take loading from pneumatic cylinder action
- Lightweight design makes it portable and easy to handle
- Heavy duty rubber base increases impact resistance and durability

74200



74201



## 74401 split tool

A hydro pneumatic power tool with separated intensifier creating a high pull force enabling the fitting of a variety of Avdel threaded inserts. The 74401's compact and ergonomic design has a long life span with low maintenance requirements.

- Split tool offering a lightweight placing head
- Designed to place threaded inserts up to M12
- The ergonomic design provides for reduced operator fatigue
- Generates high pull forces
- Longer tool life and lower maintenance

## 74405 split tool

A high performance hydro-pneumatic power tool designed for installing threaded inserts requiring more setting stroke. This tool offers a greater amount of stroke, whilst maintaining lightweight and ergonomic features as a result of the split intensifier.

- Split tool offering a lightweight placing head
- Designed to place Versa-Nut® threaded inserts up to M10
- The ergonomic design provides for reduced operator fatigue
- High placement speed for increased productivity
- Robust tool with ease to maintenance

## 74290 tool for hexagonal hole production

The 74290 tool complements and extends the range of Avdel hand tools for installing threaded inserts, by offering the capability of producing hexagonal holes for threaded Hexsert® inserts into materials where access is only possible from one side. The 74290 tool allows customers to benefit from the non-rotational properties of hexagonal inserts compared with round inserts. This is achieved by drilling a round hole, then inserting the 74290 tool and forming a hex hole.

74401



74405



74290



# Automated Assembly Systems

## Autosert®

The Autosert® automated system is a modular design for M3-M10 threaded inserts, reducing assembly time and costs. The integral processing diagnostics ensure the assembly process is highly controlled for improved product quality. The feeder bowl holds up to 2000 inserts for continuous fastener feed.

- Modular design of placing head, blow feed unit and PLC control cabinet for quick and simple integration into assembly lines. The system works as a stand-alone unit and can be used to fasten a wide range of applications.
- Flexible electric, pneumatic and hydraulic connections between the three main components for quick and simple interface with a wide range of assembly systems.
- For maximum production flexibility and minimum tool downtime the compact, lightweight placing head is quick to reconfigure, can be mounted separately and used at any angle.
- The integral processing diagnostics at all stages with clear and simple PLC displays provide for high precision, highly reliable assembly and improved product quality.



# Assembly Applications

---

## Automotive - Car Seat

---


Four Autosert® workstations with blow feed system, modular head, stockline indicator and bulk container, place 4 x M12 Hexsert® inserts per unit in a cycle time of 30 seconds. A total of 7,200 Hexsert® inserts are placed in 1800 units per day.



## Automotive - Dashboard

---

The assembly of this dashboard mounting beam, a hydroformed tube with 29 lasered hex holes, is fully automated with robots. Four Autosert® workstations with blow feed systems and modular heads place 29 x M6 and M8 Hexsert® inserts per part in a cycle time of 95 seconds.




# Assembly Workstations


## Customised Assembly Systems

### Multi-head Workstation (semi automated)

Designed for multiple and synchronous placement of threaded inserts. The example shows a station for placing 6 x M5 Hexsert® inserts for different applications, including process monitoring of part and insert presence and insert placed

diagnostic. These customised multi-head workstations can dramatically reduce assembly time and cost at improved quality.






# Eurosert® 9408



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Splined body	Fût cannelé	Gerändelter Schaft	Corpo zigrinato	Cuerpo estriado
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivaleente	Klar chromatiert, Cr6-frei	Passivazione chiara trivaleente	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	e (grip) min.	e (grip) max.	ØA +0.1/-0	ØB max.	D max.	ØJ max.	M nom.	P max.	Part No/ref
M3 x 0.5	0.25	2.00	5.00	4.95	8.20	0.75	7.40	10.50	6.00 09408-72314
M4 x 0.7	0.25	3.00	6.00	5.95	9.20	0.75	8.80	11.50	7.10 09408-72415
	3.00	4.50						13.00	
M5 x 0.8	0.25	3.00	7.00	6.95	10.20	1.00	10.20	13.00	7.90 09408-72517
	3.00	5.50						15.50	
M6 x 1.0	0.50	3.00	9.00	8.95	13.20	1.50	12.70	16.00	9.40 09408-72621
	3.00	5.50						18.50	
M8 x 1.25	0.50	3.00	11.00	10.95	16.40	1.50	15.00	17.50	11.00 09408-72822
	3.00	5.50						20.00	
M10 x 1.5	0.50	3.50	13.00	12.95	18.90	2.25	17.50	22.00	14.50 09408-72028
	3.50	6.00						25.00	

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max. torque		Nm max.		kN		Nm min.		kN	
	TORQUE APPLIED PLATE HELD STATIONARY RELATIVE TO INSERT	F	SUPPORT	SUPPORT	SPACER	SPACER	TORQUE APPLIED	SUPPORT	SUPPORT	Push-out
M3 x 0.5	1.5	4.2			1.1		1.8			
M4 x 0.7	5.1	5.5			2.2		2.9			
M5 x 0.8	7.9	8.0			3.4		4.2			
M6 x 1.0	12.4	10.8			4.7		6.5			
M8 x 1.25	32.0	12.5			6.8		7.9			
M10 x 1.5	45.0	17.3			16.7		10.7			

# Eurosert® 39002



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Stainless steel*	Inox*	Edelstahl*	Acciaio inox*	Acero inoxidable*
Natural	Brut	Blank	Nessuna finitura	Natural

\* : Werkstoff 1.4570



Thread / filetage / Gewinde / filetto / rosca	e (grip) min.	e (grip) max.	ØA +0.1/-0	ØB max.	D max.	ØJ max.	M max.	P max.	Part No/ref	
M4 x 0.7	0.25	3.00	6.0	5.95	6.70	0.46	8.80	11.30	7.10	39002-24030
M5 x 0.8	0.25	3.00	7.0	6.95	7.80	0.46	10.20	12.70	7.90	39002-25030

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	TORQUE APPLIED PLATE HELD STATIONARY RELATIVE TO INSERT	F Pull-out	SPACER TORQUE APPLIED	F Push-out
	Recommended max torque Nm max.	kN	Nm min.	kN
M4 x 0.7	5.6	9.8	1.8	1.8
M5 x 0.8	11.3	12.5	2.6	2.5

# Eurosert® 39006



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Splined body	Fût cannelé	Gerändelter Schaft	Corpo zigrinato	Cuerpo estriado
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivale	Klar chromatiert, Cr6-frei	Passivazione chiara trivale	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	e (grip)			ØA	ØB	D	ØJ	M	P	Part No/ref
	min.	max.	+0.1/-0	max.	max.	±0.13	max.	nom.	max.	
M4 x 0.7	0.25	2.00	6.00	5.97	6.70	0.46	8.80	11.30	7.10	39006-74020
M5 x 0.8	0.25	3.00	7.00	6.97	7.80	0.46	10.20	12.70	7.90	39006-75030
M6 x 1.0	0.50	3.00	9.00	8.97	10.20	0.50	12.70	15.30	9.40	39006-76030
	3.00	5.50						17.80		39006-76055
M8 x 1.25	0.50	3.50	11.00	10.97	12.20	0.63	15.00	17.30	11.00	39006-78035
	3.50	6.00						19.80		39006-78060
M10 x 1.5	1.00	3.50	13.00	12.97	14.20	0.63	17.50	20.40	14.50	39006-70035

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max. torque		Pull-out	Torque-to-turn	Push-out
	Nm max.	kN	Nm min.	kN	
M4 x 0.7	5.1	3.6	2.0	1.2	
M5 x 0.8	7.9	7.8	2.8	1.4	
M6 x 1.0	12.4	15.8	5.0	2.6	
M8 x 1.25	32.0	18.1	9.1	3.5	
M10 x 1.5	45.0	20.8	16.7	3.9	

# Nutsert® / TSN® 9468



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Stainless steel*	Inox*	Edelstahl*	Acciaio inox*	Acero inoxidable*
Natural	Brut	Blank	Nessuna finitura	Natural

\* : Werkstoff 1.4305



Thread / filetage / Gewinde / filetto / rosca	e (grip)			øA	øB	D	øJ	M	P	Part No/ref
	min.	max.	+0.1/-0	max.	max.	max.	max.	max.	max.	
M3 x 0.5	0.51	1.50	4.75	4.73	5.77	0.64	8.40	9.15	5.80	09468-00310
M4 x 0.7	0.51	2.00	6.35	6.32	7.50	0.64	10.30	10.42	7.20	09468-00413
M5 x 0.8	0.51	3.00	7.15	7.11	8.26	0.64	12.70	11.82	7.00	09468-00514
M6 x 1.0	0.76	3.25	9.53	9.50	10.85	0.77	15.50	14.61	9.50	09468-00619
M8 x 1.25	0.91	3.70	10.60	10.57	11.74	0.77	17.20	16.13	10.10	09468-05821
M10 x 1.5	1.00	3.60	14.30	14.28	15.80	0.77	23.30	18.62	10.50	09468-01023

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max torque	TORQUE APPLIED	PULL-OUT	TORQUE-TO-TURN	PUSH-OUT
		Nm max.	kN	Nm min.	kN
		4.0	8.2	0.4	1.0
M3 x 0.5		5.6	9.2	1.9	2.0
M4 x 0.7		11.3	12.0	2.6	2.7
M5 x 0.8		16.9	18.3	3.4	2.9
M6 x 1.0		22.6	24.2	3.6	3.2
M8 x 1.25		33.8	33.9	4.2	4.2
M10 x 1.5					

# Nutsert® / TSN® 9658



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a fila	Sin ala
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué,	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivale	Klar chromatiert, Cr6-frei	Passivazione chiara trivale	Pasivado claro trivalente
Lubricated	Lubrifié	Trockenfilmbeschichtet	Lubrificato	Lubricado

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	e (grip) min.	e (grip) max.	øA +0.1/-0	øA max.	øB max.	D max.	øJ max.	M max.	P max.	Part No/ref
M3 x 0.5	0.51	1.50	4.75	4.72	5.84	0.38	8.40	9.02	5.80	09658-70310
M4 x 0.7	0.51	2.00	6.35	6.32	7.30	0.51	10.30	10.41	7.20	09658-70413
M5 x 0.8	0.51	3.00	7.15	7.11	8.00	0.51	12.70	11.81	7.00	09658-70514
M6 x 1.0	0.76	3.25	9.55	9.50	10.67	0.76	15.50	14.60	9.50	09658-70619
M8 x 1.25	0.91	3.70	10.60	10.57	11.68	0.76	17.20	16.00	10.10	09658-75821
M10 x 1.5	1.00	3.60	14.20	14.17	16.20	0.76	23.30	18.50	10.50	09658-72022

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	TORQUE APPLIED PLATE HELD STATIONARY RELATIVE TO INSERT	PULL-OUT	TORQUE-TO- TURN	PUSH-OUT
	Nm max.	kN	Nm min.	kN
M3 x 0.5	1.5	2.7	0.4	0.8
M4 x 0.7	5.1	6.6	1.9	1.5
M5 x 0.8	7.9	8.0	2.6	1.9
M6 x 1.0	12.4	11.4	3.4	2.4
M8 x 1.25	16.4	15.7	3.6	2.8
M10 x 1.5	33.9	18.7	4.2	3.7

# Nutsert® / TSN® FS38



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Closed end	Borgne	Geschlossen	Fondo cieco	Fondo cerrado
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivale	Klar chromatiert, Cr6-frei	Passivazione chiara trivale	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	e (grip) min.	e (grip) max.	øA +0.1/-0	øA max.	øB max.	D max.	øJ max.	M max.	P max.	Part No/ref
M4 x 0.7	0.51	2.00	6.35	6.34	7.50	0.64	10.00	14.91	11.70	0FS38-70418
M5 x 0.8	0.51	3.00	7.15	7.13	8.26	0.64	12.20	20.26	15.50	0FS38-70521
M6 x 1.0	0.76	3.25	9.53	9.52	10.85	0.77	15.00	23.49	18.60	0FS38-70626
M8 x 1.25	0.91	3.70	10.60	10.59	11.74	0.77	16.80	23.63	18.10	0FS38-70829

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	TORQUE APPLIED	F	SPACER	F
	PLATE HELD STATIONARY WHILE TURNING TO INSERT	PULL-OUT	TORQUE-TO-TURN	PUSH-OUT
Recommended max torque				
Nm max.		kN	Nm min.	kN
M4 x 0.7	5.1	6.6	1.9	1.5
M5 x 0.8	7.9	8.0	2.6	1.9
M6 x 1.0	12.4	11.4	3.4	2.4
M8 x 1.25	16.4	15.7	3.6	2.8

# Nutsert® / TSN® FS58



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Closed end	Borgne	Geschlossen	Fondo cieco	Fondo cerrado
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivaleente	Klar chromatiert, Cr6-frei	Passivazione chiara trivaleente	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	e (grip) min.	e (grip) max.	ØA +0.1/-0	ØB max.	D ± 0.13	ØJ max.	M max.	P max.	Part No/ref
M4 x 0.7	0.50	2.50	6.10	6.05	9.30	0.80	10.50	16.64	12.10
M5 x 0.8	0.50	2.50	7.10	7.05	10.30	1.00	13.30	17.56	12.30
M6 x 1.0	0.50	3.00	9.10	9.05	13.30	1.50	15.00	22.48	16.00
M8 x 1.25	1.00	4.00	11.10	11.05	14.30	1.50	18.60	25.84	19.80

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	TORQUE APPLIED PLATE HELD STATIONARY WHILE TURNING TO INSERT	F Pull-out	SPACER TORQUE APPLIED	F Push-out
	Recommended max. torque Nm max.	kN	Nm min.	kN
M4 x 0.7	5.1	5.5	1.5	2.9
M5 x 0.8	7.9	8.0	3.0	4.2
M6 x 1.0	12.4	10.8	3.4	6.5
M8 x 1.25	16.4	12.5	5.6	7.9

# Nutsert® / TSN® FW78



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Aluminium alloy*	Alliage d'aluminium*	Aluminium*	Lega di alluminio*	Aluminio*
(2.5 % Mg)	(2.5% Mg)	(2.5 % Mg)	(2.5% Mg)	(2.5% Mg)
Natural	Brut	Blank	Nessuna finitura	Natural

\* : AA 5052, DIN 1725, AIMg2.5, Werkstoff 3.3523



Thread / filetage / Gewinde / filetto / rosca	e (grip) min.	e (grip) max.	ØA	ØB	D	ØJ	M	P	Part No/ref
M3 x 0.5	0.25	2.00	5.10	5.00	0.75	7.00	10.50	6.50	OFW78-00320
	2.00	3.00					11.50		OFW78-00330
M4 x 0.7	0.25	3.00	6.10	6.00	0.75	8.10	11.50	6.80	OFW78-00430
	3.00	4.50					13.00		OFW78-00445
M5 x 0.8	0.25	3.00	7.10	7.00	1.00	9.60	13.00	8.30	OFW78-00530
	3.00	5.50					16.00		OFW78-00555
M6 x 1.0	0.50	3.00	9.10	9.00	1.50	12.10	16.00	10.00	OFW78-00630
	3.00	5.50					18.00		OFW78-00655
	5.50	8.00					20.50		OFW78-00680
M8 x 1.25	0.50	3.00	11.10	11.00	1.50	14.50	17.50	11.50	OFW78-00830
	3.00	5.50					20.00		OFW78-00855
	5.50	8.00					23.00		OFW78-00880
M10 x 1.5	0.80	3.50	12.50	12.40	2.25	16.50	22.00	14.70	OFW78-01035
	3.50	6.00					25.00		OFW78-01060

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca					
	Recommended max. torque	Nm max.	kN	Nm min.	kN
M3 x 0.5	1.2	3.4	0.7	1.1	
M4 x 0.7	4.0	4.9	1.7	1.6	
M5 x 0.8	5.3	6.0	1.8	2.0	
M6 x 1.0	10.8	8.6	2.3	3.6	
M8 x 1.25	23.0	12.3	6.9	4.5	
M10 x 1.5	28.0	15.7	7.5	5.2	

# Nutsert® / TSN® FW96



English	Français	Deutsch	Italiano	Español
90° Countersunk	90° Tête fraisée	90° Senkkopf	90° Testa svasata	90° Cabeza avellanada
Aluminium alloy* (2.5 % Mg) Natural	Alliage d'aluminium* (2.5% Mg) Brut	Aluminium* (2.5 % Mg) Blank	Lega di alluminio* (2.5% Mg) Nessuna finitura	Aluminio* (2.5% Mg) Natural

\* : AA 5052, DIN 1725, AIMg2.5, Werkstoff 3.3523



Thread / filetage / Gewinde / filetto / rosca	e (grip)	ØA	ØB	D	ØJ	M	P	Part No/ref
	min.	max.	+0.1/-0	max.	+0/-0.4	+0.3/-0.1	max.	
M3 x 0.5	1.70	3.50	5.10	5.00	8.00	1.50	7.00	11.25
M4 x 0.7	1.70	3.50	6.10	6.00	9.00	1.50	8.10	11.50
	3.50	5.00						6.80
M5 x 0.8	1.70	4.00	7.10	7.00	10.00	1.50	9.60	13.00
	4.00	6.50						16.00
M6 x 1.0	1.70	4.50	9.10	9.00	12.00	1.50	12.10	17.00
	4.50	6.50						19.00
M8 x 1.25	1.70	4.50	11.10	11.00	14.00	1.50	14.50	19.00
	4.50	6.50						21.00
M10 x 1.5	1.70	4.50	12.50	12.40	15.40	1.50	16.50	21.00
	4.50	6.50						14.70
								OFW96-01045
								OFW96-01065

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max torque	TORQUE APPLIED	PULL-OUT	TORQUE-TO-TURN	PUSH-OUT
		Nm max.	kN	Nm min.	kN
M3 x 0.5	1.2	3.7	0.8	1.4	
M4 x 0.7	4.0	4.7	1.7	1.9	
M5 x 0.8	5.3	6.3	2.2	2.6	
M6 x 1.0	10.8	10.1	4.7	3.4	
M8 x 1.25	23.0	11.7	7.8	3.7	
M10 x 1.5	28.0	13.8	9.9	4.7	

# Nutsert® / TSN® GM17



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Aluminium alloy*	Alliage d'aluminium*	Aluminium*	Lega di alluminio*	Aluminio*
(2.5 % Mg)	(2.5% Mg)	(2.5 % Mg)	(2.5% Mg)	(2.5% Mg)
Natural	Brut	Blank	Nessuna finitura	Natural

\* : AA 5052, DIN 1725, AIMg2.5, Werkstoff 3.3523



Thread / filetage / Gewinde / filetto / rosca	e (grip) min.	e (grip) max.	øA +0.1/-0	øB max.	D +0.3/-0.2	øJ +0.3/-0.1	M max.	P max.	Part No/ref
M4 x 0.7	0.50	3.00	6.10	6.00	6.50	0.50	8.10	10.75	6.80
M5 x 0.8	0.50	3.00	7.10	7.00	7.50	0.50	9.60	12.00	8.30
M6 x 1.0	0.50	3.00	9.10	9.00	9.50	0.50	12.10	14.50	10.00
M8 x 1.25	0.50	3.00	11.10	11.00	11.50	0.50	14.50	16.00	11.50

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	TORQUE APPLIED PLATE HELD STATIONARY RELATIVE TO INSERT	PULL-OUT	TORQUE-TO-TURN	PUSH-OUT
	Recommended max torque Nm max.	kN	Nm min.	kN
M4 x 0.7	4.0	3.7	1.6	0.7
M5 x 0.8	5.3	5.4	2.1	0.8
M6 x 1.0	10.8	8.5	2.4	0.9
M8 x 1.25	23.0	13.1	5.4	1.0

# Nutsert® / TSN® GM57



English	Français	Deutsch	Italiano	Español
90° Countersunk	90° Tête fraisée	90° Senkkopf	90° Testa svasata	90° Cabeza avellanada
Closed end	Borgne	Geschlossen	Fondo cieco	Fondo cerrado
Aluminium alloy*	Alliage d'aluminium*	Aluminium*	Lega di alluminio*	Aluminio*
(2.5 % Mg)	(2.5% Mg)	(2.5 % Mg)	(2.5% Mg)	(2.5% Mg)
Natural	Brut	Blank	Nessuna finitura	Natural

\* : AA 5052, DIN 1725, AIMg2.5, Werkstoff 3.3523



Thread / filetage / Gewinde / filetto / rosca	e (grip)		■	ØA	ØB	D	ØJ	M	P	Part No/ref
	min.	max.		max.	+0/-0.4	+0.3/-0.1	max.	± 0.35	max.	
M4 x 0.7	1.70	3.50	6.10	6.00	9.00	1.50	8.10	15.50	10.80	0GM57-00435
	3.50	5.00						17.00		0GM57-00450
M5 x 0.8	1.70	4.00	7.10	7.00	10.00	1.50	9.60	18.00	14.30	0GM57-00540
	4.00	6.50						20.50		0GM57-00565
M6 x 1.0	1.70	4.50	9.10	9.00	12.00	1.50	12.10	22.00	17.50	0GM57-00645
	4.50	6.50						24.00		0GM57-00665
M8 x 1.25	1.70	4.50	11.10	11.00	14.00	1.50	14.50	25.00	19.00	0GM57-00845
	4.50	6.50						28.00		0GM57-00865

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max torque Nm max.	Pull-out kN	Torque-to-turn Nm min.	Push-out kN		
					TORQUE APPLIED PUSH HELD STATICALLY RELATIVE TO INSERT 	PULL OUT 
M4 x 0.7	4.0	4.7	1.7	1.9		
M5 x 0.8	5.3	6.3	2.2	2.6		
M6 x 1.0	10.8	10.1	4.7	3.4		
M8 x 1.25	23.0	11.7	7.8	3.7		

# Nutsert® / TSN® GM68



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Closed end	Borgne	Geschlossen	Fondo cieco	Fondo cerrado
Aluminium alloy*	Alliage d'aluminium*	Aluminium*	Lega di alluminio*	Aluminio*
(2.5 % Mg)	(2.5% Mg)	(2.5 % Mg)	(2.5% Mg)	(2.5% Mg)
Natural	Brut	Blank	Nessuna finitura	Natural

\* : AA 5052, DIN 1725, AIMg2.5, Werkstoff 3.3523



Thread / filetage / Gewinde / filetto / rosca	e (grip)			ØA	ØB	D	ØJ	M	P	Part No/ref
	min.	max.		max.	±0.35	±0.15	max.	± 0.35	max.	
M3 x 0.5	0.25	2.00	5.10	5.00	8.00	0.75	7.00	14.00	10.00	0GM68-00320
M4 x 0.7	0.25	3.00	6.10	6.00	10.00	0.75	8.10	15.50	10.80	0GM68-00430
	3.00	4.50						17.00		0GM68-00445
M5 x 0.8	0.25	3.00	7.10	7.00	11.00	1.00	9.60	19.00	14.30	0GM68-00530
	3.00	5.50						21.50		0GM68-00555
M6 x 1.0	0.50	3.00	9.10	9.00	13.00	1.50	12.10	23.00	17.50	0GM68-00630
	3.00	5.50						26.00		0GM68-00655
M8 x 1.25	0.50	3.00	11.10	11.00	16.00	1.50	14.50	24.00	19.00	0GM68-00830
	3.00	5.50						27.00		0GM68-00855


all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

Thread / filetage / Gewinde / filetto / rosca	Recommended max torque Nm max.	Pull-out kN	Torque-to-turn Nm min.	Push-out kN	TORQUE APPLIED	SUPPORT	SPACER	SUPPORT
M3 x 0.5	1.2	3.4	0.7	1.1				
M4 x 0.7	4.0	4.9	1.7	1.6				
M5 x 0.8	5.3	6.0	1.8	2.0				
M6 x 1.0	10.8	8.6	2.3	3.6				
M8 x 1.25	23.0	12.3	6.9	4.5				

# DK DKA



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a fila	Sin ala
Splined body	Fût cannelé	Gerändelter Schaft	Corpo zigrinato	Cuerpo estriado
Aluminium Clear protective coating	Aluminium Couche protectrice claire	Aluminium Klare Schutzschicht	Aluminium Strato protezione chiaro	Aluminium Capa protectora clara




Thread / filetage / Gewinde / filetto / rosca	e (grip)			øA	øB	D	øJ	M	P	Part No/ref
	min.	max.		max.	±0.25	±0.05	max.	±0.38	max.	
M4 x 0.7 6H	0.5	2.0		6.75	6.73	7.87	9.91	10.67	7.75	DKA-470-2.0
	2.0	3.3						11.94		DKA-470-3.3
M5 x 0.8 6H	0.5	3.3		7.60	7.52	8.64	11.43	12.07	8.00	DKA-580-3.3
	3.3	5.7						14.86		DKA-580-5.7
M6 x 1.0 6H	0.7	4.2		10.00	9.91	11.56	13.97	14.73	9.65	DKA-610-4.2
	4.2	6.6						17.27		DKA-610-6.6
M8 x 1.25 6H	0.7	3.8		13.50	13.46	15.11	18.80	17.53	11.94	DKA-8125-3.8
	3.8	7.9						20.45		DKA-8125-7.9
M10 x 1.5 6H	0.7	3.8						17.53		DKA-1015-3.8
	3.8	7.9						20.45		DKA-1015-7.9

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a fila	Sin ala
Splined body	Fût cannelé	Gerändelter Schaft	Corpo zigrinato	Cuerpo estriado
Steel	Acier	Stahl	Acciaio	Acero
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivalente	Klar chromatiert, Cr6-frei	Passivazione chiara trivalente	Pasivado claro trivalente



Thread / filetage / Gewinde / filetto / rosca	e (grip)			ØA	ØB	D	ØJ	M	P	Part No/ref
	min.	max.		max.	±0.25	±0.05	max.	±0.38	max.	
M4 x 0.7 6H	0.5	2.0		6.75	6.73	7.87	9.91	10.67	7.75	DKS-470-2.0
	2.0	3.3						11.94		DKS-470-3.3
M5 x 0.8 6H	0.5	3.3		7.60	7.52	8.64	11.43	12.07	8.00	DKS-580-3.3
	3.3	5.7						14.86		DKS-580-5.7
M6 x 1.0 6H	0.7	4.2		10.00	9.91	11.56	13.97	14.73	9.65	DKS-610-4.2
	4.2	6.6						17.27		DKS-610-6.6
M8 x 1.25 6H	0.7	3.8		13.50	13.46	15.11	18.80	17.53	11.94	DKS-8125-3.8
	3.8	7.9						20.45		DKS-8125-7.9
M10 x 1.5 6H	0.7	3.8					18.80	17.53	11.94	DKS-1015-3.8
	3.8	7.9						20.45		DKS-1015-7.9


all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

Thread / filetage / Gewinde / filetto / rosca					
	Nm	kN	Nm	kN	
M4 x 0.7 6H	6.2	2.3	1.1	0.8	
M5 x 0.8 6H	10.7	2.8	1.4	1.5	
M6 x 1.0 6H	18.1	3.0	1.4	1.4	
M8 x 1.25 6H	N/A	5.0	2.7	2.3	
M10 x 1.5 6H	N/A	5.0	2.7	2.3	

# DL DLA



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Splined body	Fût cannelé	Gerändelter Schaft	Corpo zigrinato	Cuerpo estriado
Aluminium Clear protective coating	Aluminium Couche protectrice claire	Aluminium Klare Schutzschicht	Aluminium Strato protezione chiaro	Aluminium Capa protectora clara




Thread / filetage / Gewinde / filetto / rosca	e (grip)			ØA	ØB	D	ØJ	M	P	Part No/ref
	min.	max.	+0.15/-0	max.	±0.25	±0.08	max.	±0.38	max.	
M4 x 0.7 6H	0.5	2.0	6.80	6.75	9.91	9.91	10.67	7.75	DLA-470-2.0	
	2.0	3.3					11.94			DLA-470-3.3
M5 x 0.8 6H	0.5	3.3	7.60	7.55	10.54	11.43	12.07	8.00	DLA-580-3.3	
	3.3	5.7					14.86			DLA-580-5.7
M6 x 1.0 6H	0.7	4.2	10.00	9.90	12.70		14.73	9.65	DLA-610-4.2	
	4.2	6.6					17.27			DLA-610-6.6
M8 x 1.25 6H	0.7	3.8	13.50	13.45	17.40	0.89	17.53	11.94	DLA-8125-3.8	
	3.8	7.9					20.45			DLA-8125-7.9
M10 x 1.5 6H	0.7	3.8					17.53	11.94	DLA-1015-3.8	
	3.8	7.9					20.45			DLA-1015-7.9

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

# DL DLS



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Splined body	Fût cannelé	Gerändelter Schaft	Corpo zigrinato	Cuerpo estriado
Steel	Acier	Stahl	Acciaio	Acero
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivalente	Klar chromatiert, Cr6-frei	Passivazione chiara trivalente	Pasivado claro trivalente



Thread / filetage / Gewinde / filetto / rosca	e (grip)			ØA	ØB	D	ØJ	M	P	Part No/ref
	min.	max.		max.	±0.25	±0.08	max.	±0.38	max.	
M4 x 0.7 6H	0.5	2.0		6.80	6.75	9.91	9.91	10.67	7.75	DLS-470-2.0
	2.0	3.3						11.94		DLS-470-3.3
M5 x 0.8 6H	0.5	3.3		7.60	7.55	10.54	11.43	12.07	8.00	DLS-580-3.3
	3.3	5.7						14.86		DLS-580-5.7
M6 x 1.0 6H	0.7	4.2		10.00	9.90	12.70		14.73	9.65	DLS-610-4.2
	4.2	6.6						17.27		DLS-610-6.6
M8 x 1.25 6H	0.7	3.8		13.50	13.45	17.40	0.89	17.53	11.94	DLS-8125-3.8
	3.8	7.9						20.45		DLS-8125-7.9
M10 x 1.5 6H	0.7	3.8					13.97	17.53	11.94	DLS-1015-3.8
	3.8	7.9						20.45		DLS-1015-7.9

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca					
	Nm	kN	Nm	kN	
M4 x 0.7 6H	6.2	2.3	1.1	0.8	
M5 x 0.8 6H	10.7	2.8	1.4	1.5	
M6 x 1.0 6H	18.1	3.0	1.4	1.4	
M8 x 1.25 6H	N/A	5.0	2.7	2.3	
M10 x 1.5 6H	N/A	5.0	2.7	2.3	

# Hexsert® 9498



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Hexagonal body	Hexagonal corps	Hexagonaler Schaft	Hexagonal corpo	Hexagonal cuerpo
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué,	Verzinkt	Zincatura spessore	Zincado
Clear trivalent passivated	Passivation claire trivaleente	Klar chromatiert, Cr6-frei	Passivazione chiara trivaleente	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	A/F rec. min.	A/F rec. max.	e (grip) min.	e (grip) max.	ØA ± 0.08	ØB max.	D ± 0.13	F ± 0.08	ØJ max.	M ± 0.50	P max.	Part No/ref
M4 x 0.7	6.00	6.10	0.50	2.00	5.89	9.17	1.00	5.89	9.20	10.00	5.00	09498-72415
M5 x 0.8	7.00	7.10	0.50	3.00	6.89	10.17	1.00	6.89	11.20	13.20	6.80	09498-72516
			3.00	5.50						15.70		09498-72520
M6 x 1.0	9.00	9.10	0.50	3.00	8.89	13.20	1.50	8.89	13.40	15.50	10.10	09498-72620
M8 x 1.25	11.00	11.10	0.50	3.00	10.89	16.28	1.50	10.89	16.20	18.00	11.40	09498-72823
			3.00	5.50						20.5		09498-72826
M10 x 1.5	13.00	13.10	1.00	3.50	12.89	19.10	2.00	12.89	18.50	21.0	13.20	09498-72026
M12 x 1.75	16.00	16.10	1.50	4.50	15.89	23.30	2.25	15.89	23.60	27.8	17.00	09498-72235

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max torque		Pull-out	Torque-to-turn	Push-out
	Nm max.	kN	Nm min.	kN	
M4 x 0.7	5.1	6.3	4.5	2.2	
M5 x 0.8	7.9	8.8	8.6	3.6	
M6 x 1.0	12.4	14.4	11.9	5.3	
M8 x 1.25	32.0	15.0	25.0	8.0	
M10x 1.5	45.0	19.7	45.2	9.2	
M12 x 1.75	60.0	21.3	58.0	10.2	

# Hexsert® 9688



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Hexagonal body	Hexagonal corps	Hexagonaler Schaft	Hexagonal corpo	Hexagonal cuerpo
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué,	Verzinkt	Zincatura spessa	Zincado
Clear trivalent passivated	Passivation claire trivale	Klar chromatiert, Cr6-frei	Passivazione chiara	Pasivado claro trivalente
Lubricated	Lubrifié	Trockenfilmbeschichtet	trivale	Lubricado

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	A/F min.	A/F max.	e (grip) min.	e (grip) max.	φA max.	B max.	D max.	F max.	φJ min. e	φJ max. e	M max.	P max.	Part No/ref
M3 x 0.5	4.80	4.85	0.70	1.63	4.72	6.10	0.45	4.81	6.90	6.40	9.02	5.40	09688-70310
M4 x 0.7	6.38	6.43	0.51	1.63	6.33	8.00	0.69	6.37	10.00	8.70	10.42	7.40	09688-70413
M5 x 0.8	7.32	7.37	0.51	2.03	7.14	9.22	0.72	7.26	12.20	10.70	11.82	7.20	09688-70514
M6 x 1.0	9.65	9.70	0.76	2.92	9.53	11.94	0.89	9.64	15.00	12.70	14.61	9.70	09688-70619
M8 x 1.25	10.70	10.80	0.91	3.25	10.50	12.96	0.89	10.67	16.60	14.30	16.00	10.50	09688-70821

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max torque		Pull-out		Torque-to-turn		Push-out	
	Nm max.	kN	Nm min.	kN	SPACER	SPACER	SUPPORT	SUPPORT
M3 x 0.5	1.5	2.9	1.0	0.8				
M4 x 0.7	5.1	4.2	4.0	1.3				
M5 x 0.8	7.9	5.9	6.6	1.9				
M6 x 1.0	12.4	6.9	8.7	2.4				
M8 x 1.25	16.4	14.8	11.8	2.8				

# Euro Hexsert® 39101



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Hexagonal body	Hexagonal corps	Hexagonaler Schaft	Hexagonal corpo	Hexagonal cuerpo
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivale	Klar chromatiert, Cr6-frei	Passivazione chiara trivale	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	A/F	e (grip)	øA	B	D	F	øJ	M	P	Part No/ref
M4 x 0.7	6.0	0.50	2.00	5.89	7.80	0.69	5.89	9.20	10.50	6.00 39101-74020
M5 x 0.8	7.0	0.50	3.00	6.89	9.10	0.77	6.89	11.20	12.70	8.60 39101-75030
M6 x 1.0	9.0	0.50	3.00	8.89	11.60	0.91	8.89	13.40	15.00	10.10 39101-76030
M8 x 1.25	11.0	0.50	3.00	10.89	14.20	1.07	10.89	16.20	17.50	11.40 39101-78030
M10 x 1.5	13.0	1.00	3.50	12.89	16.40	1.07	12.89	18.50	20.20	13.20 39101-70035

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	TORQUE APPLIED PLATE HELD STATIONARY RELATIVE TO INSERT	PULL-OUT	SPACER SPACER TORQUE APPLIED	PUSH-OUT
	Nm max.	kN	Nm min.	kN
M4 x 0.7	5.1	6.3	4.2	1.4
M5 x 0.8	7.9	8.8	7.5	2.6
M6 x 1.0	12.4	14.4	10.7	3.2
M8 x 1.25	32.0	15.0	22.7	4.1
M10 x 1.5	45.0	19.7	38.5	5.2

# Euro Hexsert® 39102



English	Français	Deutsch	Italiano	Español
Low profile	Auto-affleurante	Extra kleiner Kopf	Testa a filo	Sin ala
Hexagonal body	Hexagonal corps	Hexagonaler Schaft	Hexagonal corpo	Hexagonal cuerpo
Stainless steel*	Inox*	Edelstahl*	Acciaio inox*	Acero inoxidable*
Natural	Brut	Blank	Nessuna finitura	Natural

\* : BS 111 394S17, Werkstoff 1.4567



Thread / filetage / Gewinde / filetto / rosca	A/F	e (grip)	øA	B	D	F	øJ	M	P	Part No/ref
	+0.1/-0	min.	max.	± 0.08	max.	± 0.13	± 0.08	max.	± 0.50	
M6 x 1.0	9.0	0.50	3.00	8.91	11.60	0.84	8.91	13.20	15.00	39102-26030
		3.00	5.50						10.10	39102-26055

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	TORQUE APPLIED PLATE HELD STATIONARY RELATIVE TO INSERT	PULL-OUT	TORQUE-TO-TURN	PUSH-OUT
	Nm max.	kN	Nm min.	kN
39102-26030	16.9	16.4	12.5	4.1
39102-26055	16.9	22.0	25.0	4.1

# Euro Hexsert® 49141



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Hexagonal body	Hexagonal corps	Hexagonaler Schaft	Hexagonal corpo	Hexagonal cuerpo
Closed end	Borgne	Geschlossen	Fondo cieco	Fondo cerrado
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué,	Verzinkt	Zincatura spessore	Zincado
Clear trivalent passivated	Passivation claire trivalente	Klar chromatiert, Cr6-frei	Passivazione chiara trivalente	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	A/F rec. min.	A/F rec. max.	e (grip) min.	e (grip) max.	øA	øB	D	F	øJ	M	P	Part No/ref
M6 x 1.0	9.00	9.10	0.50	3.00	8.89	13.20	1.50	8.89	13.40	27.30	17.80	49141-76030
M8 x 1.25	11.00	11.10	0.50	3.00	10.89	16.28	1.50	10.89	16.20	28.00	20.10	49141-78030


all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

Thread / filetage / Gewinde / filetto / rosca	Recommended max torque	Pull-out	Torque-to-turn	Push-out
	Nm max.	kN	Nm min.	kN
M6 x 1.0	12.4	14.4	11.9	5.3
M8 x 1.25	32.0	15.0	25.0	8.0


# High Strength Hexsert® 39301



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Hexagonal body	Hexagonal corps	Hexagonaler Schaft	Hexagonal corpo	Hexagonal cuerpo
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivaleente	Klar chromatiert, Cr6-frei	Passivazione chiara trivaleente	Pasivado claro trivalente



\*: DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008  
 \*\*: to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo  
 (ASTM B117)



Thread / filetage / Gewinde / filetto / rosca	A/F	e (grip)	øA	øB	D	F	øJ	M	P	Part No/ref
	min.	max.	min.	max.	±0.08	min.	max.	nom.	max.	
M6 x 1.0	9.0	9.1	0.5	3.0	8.89	12.80	13.20	1.50	8.89	18.8 39301-26030
M8 x 1.25	11.0	11.1	0.5	3.0	10.89	15.68	16.28	1.50	10.89	20.4 39301-28030
M10 x 1.5	13.0	13.1	1.0	3.5	12.89	18.50	19.10	2.00	12.89	26.0 39301-20035
M12 x 1.75	16.0	16.1	1.0	4.0	15.88	22.60	23.30	2.25	15.90	30.8 39301-22040

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


Thread / filetage / Gewinde / filetto / rosca	Recommended max torque		Pull-out		Torque-to-turn		Push-out		e max. kN
	max. Nm	e max. kN	max. Nm	e min. Nm	max. kN				
M6 x 1.0	17.0	20.6	24.7	14.4	7.1				
M8 x 1.25	60.0	28.1	34.6	15.6	10.7				
M10 x 1.5	100.0	34.2	62.0	60.8	12.5				
M12 x 1.75	135.0	40.9	135.0	62.0	18.3				

# Squaresert® GK08



English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Square section	Corps carré	Vierkantschaft	Corpo quadrati	Cuerpo cuadrado
Low carbon steel*	Acier bas carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivaleente	Klar chromatiert, Cr6-frei	Passivazione chiara trivaleente	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008



Thread / filetage / Gewinde / filetto / rosca	e (grip)		A/F	ØA	B	D	J	M	P	Part No/ref
	min.	max.								
M5 x 0.8	0.50	1.50	7.30	7.10	10.90	0.65	10.40	11.40	8.20	OGK08-72514
	1.50	3.00						13.00		OGK08-72516
M6 x 1.0	0.50	2.00	9.30	9.10	13.50	0.95	13.50	15.50	9.90	OGK08-72619
	2.00	4.00						17.50		OGK08-72622
M8 x 1.25	1.00	3.00	11.30	11.10	18.00	1.65	16.40	18.90	11.80	OGK08-72823

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

Thread / filetage / Gewinde / filetto / rosca	Recommended max. torque		Pull-out	Torque-to-turn	Push-out
	Nm max.	kN	Nm min.	kN	
M5 x 0.8	7.9	5.5	10.2	2.4	
M6 x 1.0	12.4	7.3	15.4	4.6	
M8 x 1.25	32.0	10.5	34.0	6.5	

# Versa-Nut® VN21




English	Français	Deutsch	Italiano	Español
Large flange	A collarette	Flachkopf	Flangiato	Ala Ancha
Slotted body	Corps préfendu	Geschlitzte Hülse	Corpo fessurato	Cuerpo ranurado
Low carbon steel*	Acier à faible teneur en carbone*	Stahl*	Acciaio a basso tenore di carbonio*	Acero bajo en carbono*
Zinc plated	Revêtement zingué	Verzinkt	Zincato	Zincado
Clear trivalent passivated	Passivation claire trivalente	Klar chromatiert, Cr6-frei	Passivazione chiara trivalente	Pasivado claro trivalente

\* : DIN EN 10263-2 Qst 34-3, BS EN/DIN 10263-2 C8C, Werkstoff 1.0213, SAE 1008

\*\*: to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo (ASTM B117)

\*\*\*: to white rust / à la rouille blanche / bis Weißrost / alla ruggine bianca / al óxido blanco

240 h\*\*/96 h\*\*\*



Thread / filetage / Gewinde / filetto / rosca					ø A	ø B	D	J	M	P		Part No/ref
	min.	max.	min.	max.								
M4 x 0.7	0.50	3.80	6.13	6.25	6.12	11.34	1.09	14.0	18.01	8.60	5.1	OVN21-02422
	3.80	6.85							21.16			OVN21-02426
M5 x 0.8	0.50	4.45	7.48	7.62	7.47	12.95	1.09	18.0	22.39	9.90	7.9	OVN21-02528
	4.45	8.10							25.16			OVN21-02531
M6 x 1.0	0.50	7.10	8.80	8.93	8.79	16.12	1.63	22.0	27.30	12.80	12.4	OVN21-02634
	7.10	12.70							33.22			OVN21-02641
M8 x 1.25	0.50	7.10	11.11	11.50	11.10	19.29	1.70	26.0	30.92	14.47	32.0	OVN21-02838
	7.10	12.70							36.87			OVN21-02846

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros


1) Recommended maximum torque as applied to a joint with a static top plate. Thread of insert will not be damaged. However this torque value may exceed the strength of the screw or bolt in question. Always refer to the recommended tightening torque limits for the screw or bolt.

Couple maximum recommandé pour un assemblage avec plaque supérieure statique. Le filet de l'insert reste intact. Ce couple peut néanmoins dépasser la résistance de la vis ou du boulon en question. Veillez toujours à vous référer aux limites de couple de serrage recommandées pour la vis ou le boulon.

Empfohlenes maximales Drehmoment für eine Verbindung bei der das obere an die Mutter anzuschraubende Bauteil fest eingespannt ist. Das Gewinde wird nicht beschädigt. Möglicherweise übersteigt dieser Anzugswert die Festigkeit der Schraube. Beziehen Sie sich immer auf die max. Anzugswerte der Schraube.

Coppia massima raccomandata applicata a una giuntura con piastra superiore statica. La filettatura dell'inserto non verrà danneggiata, comunque questa coppia può superare la resistenza della vite o del vullone impegato. Verificare sempre le coppie di serraggio raccomandate della vite o bullone impiegato.

Par máximo recomendado aplicado a la unión con la placa superior estática. La rosca del inserto no queda dañada. Sin embargo este valor de par puede superar la resistencia del perno o tornillo en cuestión. Siempre consultar los límites de par de apriete recomendados para el perno o tornillo.



---

## The Range of Avdel® Blind Fastening Systems

---



### Speed Fastening® Systems

Extra fast and reliable fastening from one side. Because rivets are fed automatically.



### Breakstem Systems

Blind fastening systems with various features. From multi-grip rivet up to high strength stainless steel rivet.



### Lockbolt Systems

For joints with highest impact. High clamp force and vibration resistance.



### Blind Threaded Inserts

Fast system for sustainable threads with high torque-to-turn.



### Installation Equipment

From manually operated handtools to customised assembly workstations.

# Holding your world together®

## AUSTRALIA

Infastech (Australia) Pty Ltd.  
891 Wellington Road  
Rowville  
Victoria 3178  
Tel: +61 3 9765 6400  
Fax: +61 3 9765 6445  
info@infastech.com.au

## CANADA

Avdel Canada Limited  
1030 Lorimar Drive  
Mississauga  
Ontario L5S 1R8  
Tel: +1 905 364 0664  
+800 268 9947 toll-free  
Fax: +1 905 364 0678  
+800 594 7661 toll-free  
infoAvdel-Canada@infastech.com

## CHINA

Infastech (China) Ltd.  
RM 1708, 17/F., Nanyang Plaza,  
57 Hung To Rd., Kwun Tong  
Hong Kong  
Tel: +852 2950 0631  
Fax: +852 2950 0022  
infochina@infastech.com

## FRANCE

Avdel France S.A.S.  
33 bis, rue des Ardennes  
BP4  
75921 Paris Cedex 19  
Tel: +33 (0) 1 4040 8000  
Fax: +33 (0) 1 4208 2450  
AvdelFrance@infastech.com

## GERMANY

Avdel Deutschland GmbH  
Klusriede 24  
30851 Langenhagen  
effective December 2011:  
Rotenburger Str. 28  
30659 Hannover  
Tel: +49 (0) 511 7288 0  
Fax: +49 (0) 511 7288 133  
AvdelDeutschland@infastech.com

## INDIA

Infastech Fastening Technologies  
India Private Limited  
Plot No OZ-14, Hi Tech SEZ,  
SIPCOT Industrial Growth Center,  
Oragadam, Sriperumbudur Taluk,  
Kanchipuram District,  
602105 Tamilnadu

Tel: +91 44 4711 8001  
Fax: +91 44 4711 8009  
info-in@infastech.com

## ITALY

Avdel Italia srl  
Viale Lombardia 51/53  
20861 Brugherio (MB)  
Tel: +39 039 289911  
Fax: +39 039 2873079  
vendite@infastech.com

## JAPAN

Infastech Kabushiki Kaisha  
Center Minami SKY,  
3-1 Chigasaki-Chuo, Tsuzuki-ku,  
Yokohama-city,  
Kanagawa Prefecture  
Japan 224-0032

Tel: +81 45 947 1200  
Fax: +81 45 947 1205  
info@infastech.co.jp

## MALAYSIA

Infastech (Malaysia) Sdn Bhd  
Lot 63, Persiaran Bunga Tanjung 1,  
Senawang Industrial Park  
70400 Seremban  
Negeri Sembilan  
Tel: +606 676 7168  
Fax: +606 676 7101  
info-my@infastech.com

## SINGAPORE

Infastech (Singapore) Pte Ltd.  
31 Kaki Bukit Road 3  
#05-03/06 Techlink  
Singapore, 417818  
Tel: +65 6372 5653  
Fax: +65 6744 5643  
info-sg@infastech.com

## SOUTH KOREA

Infastech (Korea) Ltd.  
212-4, Suyang-Ri,  
Silchon-Eup, Kwangju-City,  
Kyunggi-Do, Korea, 464-874  
Tel: +82 31 798 6340  
Fax: +82 31 798 6342  
info@infastech.co.kr

## SPAIN

Avdel Spain S.A.  
C/ Puerto de la Morcuera, 14  
Polígono Industrial Prado Oveta  
Ctra. de Toledo, km 7.8  
28919 Leganés (Madrid)  
Tel: +34 91 3416767  
Fax: +34 91 3416740  
ventas@infastech.com

## TAIWAN

Infastech/Tri-Star Limited  
No 269-7, Baodong Rd,  
Guanmiao Dist.,  
Tainan City  
Taiwan, R.O.C 71841  
Tel: +886 6 596 5798 (ext 201)  
Fax: +886 6 596 5758  
info-tw@infastech.com

## THAILAND

Infastech Thai Co., Ltd.  
64/132 Moo 4 Tambon Pluakdaeng  
Amphur Pluakdaeng Rayong  
21140 Thailand  
Tel: +66 (0) 38 656360  
Fax: +66 (0) 38 656346  
info-th@infastech.com

## UNITED KINGDOM

Avdel UK Limited  
Pacific House  
2 Swiftfields  
Watchmead Industrial Estate  
Welwyn Garden City  
Hertfordshire AL7 1LY  
Tel: +44 (0) 1707 292000  
Fax: +44 (0) 1707 292199  
enquiries@infastech.com

## USA

Avdel USA LLC  
614 NC Highway 200 South  
Stanfield, North Carolina 28163  
Tel: +1 704 888 7100  
Fax: +1 704 888 0258  
infoAvdel-USA@infastech.com

## Infastech (Decorah) LLC

1304 Kerr Drive  
Decorah, IA 52101  
Tel: +1 563 382 4216  
Fax: +1 563 387 3540

Your local distributor for Avdel® Blind Threaded Inserts is:



[www.avdel-global.com](http://www.avdel-global.com)  
[www.infastech.com](http://www.infastech.com)

Autosert®, Avdel®, Eurosert®, Hexsert®, Nutsert®, Squaresert®, TSN®, Nutsert SQ®, Speed Fastening®, Versa-Nut® and Holding your world together® are registered trademarks of Avdel UK Limited. Rimlex® is a registered trademark of Inlex Locking Limited Corporation. Infastech™ and Our Technology, Your Success™ are trademarks of Infastech Intellectual Properties Pte Ltd. The names and logos of other companies mentioned herein may be trademarks of their respective owners. This document is for informational purposes only. Infastech makes no warranties, expressed or implied, in this document. Data shown is subject to change without prior notice as a result of continuous product development and improvement policy. Your local Avdel representative is at your disposal should you need to confirm latest information.