

**RTV630
Silicone Moldmaking Material - Component A****1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION**

Manufacturer Name: Momentive performance material
260 Hudson River Rd
Waterford NY 12188

Revised: 09/08/2011
Prepared by PRODUCT STEWARDSHIP COMPLIANCE AND STANDARDS
CHEMTREC 1-800-424-9300

Chemical Family/Use: Silicone Elastomer
Formula: Mixture

HMIS

FLAMMABILITY: 1 Reactivity: 0 Health: 0

NFPA

Flammability: 1 Reactivity: 0 Health: 1

2. HAZARDS IDENTIFICATION**EMERGENCY OVERVIEW**

CAUTION! May cause skin, eye, and respiratory tract irritation. Attention: Not for injection into humans.

Form: Liquid

Color: Pale yellow

Odor: Faint

POTENTIAL HEALTH EFFECTS**INGESTION**

None known. Not an anticipated route of exposure.

SKIN

May cause skin irritation.

INHALATION

May cause respiratory irritation.

EYES.

May cause eye irritation.

MEDICAL CONDITIONS AGGRAVATED

None known.

SUBCHRONIC (TARGET ORGAN)

None known.

**RTV630
Silicone Moldmaking Material - Component B****1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION**

Manufacturer Name: Momentive performance material
260 Hudson River Rd
Waterford NY 12188

Revised: 07/05/2012
Prepared by Product Regulatory Compliance
CHEMTREC 1-800-424-9300
MSDS Contact 1-888-443-9466
Information 4information@momentive.com

Chemical Family/Use: Silicone Rubber

Formula: Mixture

HMIS

Health: 0 Flammability: 1 Reactivity: 1

NFPA

Health: 1 Flammability: 1 Reactivity: 1

2. HAZARDS IDENTIFICATION**EMERGENCY OVERVIEW**

CAUTION! Product generates flammable gas on contact with acids, bases or oxidizing substances.

Form: Liquid

Form: Blue

Odor: Faint

POTENTIAL HEALTH EFFECTS**INGESTION**

None known.

SKIN

Causes mild skin irritation.

INHALATION

None known.

EYES

May cause eye irritation.

MEDICAL CONDITIONS AGGRAVATED

None known.

**RTV630
Silicone Moldmaking Material - Component B****SUBCHRONIC (TARGET ORGAN)**

None known.

CHRONIC EFFECTS / CARCINOGENICITY

This product or one of its ingredients present at 0.1% or more is NOT listed as a carcinogen or suspected carcinogen by NTP, IARC, or OSHA.

ROUTES OF EXPOSURE

None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

<u>PRODUCT COMPOSITION</u>	<u>CAS-No.</u>	<u>WGT. %</u>
<u>A. HAZARDOUS</u>		
METHYLHYDROGENPOLYSILOXANE	68988-57-8	30 - 60 %
<u>B. NON-HAZARDOUS</u>		
polyvinylsiloxane	68083-19-2	30 - 60 %
Polyalkylalkenylsiloxane	68584-83-8	10 - 30 %

4. FIRST AID MEASURES**INGESTION**

Rinse mouth thoroughly. Get medical attention.

SKIN

After contact with skin, remove product mechanically. Wash area with soap and water.

INHALATION

None known.

EYES

Rinse the eye with water immediately. If eye irritation persists: Get medical advice/attention.

**RTV630
Silicone Moldmaking Material - Component B****NOTE TO PHYSICIAN**

None known.

5. FIRE-FIGHTING MEASURES

FLASH POINT: > 100 °C; 212 °F
FLAMMABLE LIMITS LEL: Not applicable
FLAMMABLE LIMITS UEL: Not applicable

SENSITIVITY TO MECHANICAL IMPACT: No

EXTINGUISHING MEDIA

Carbon dioxide, Foam., Water spray

SPECIAL FIRE FIGHTING PROCEDURES

Firefighters must wear NIOSH/MSHA approved positive pressure self-contained breathing apparatus with full face mask and full protective clothing.

FURTHER INFORMATION

Use standard firefighting procedures and consider the hazards of other involved materials.

6. ACCIDENTAL RELEASE MEASURES**ACTION TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED**

Wipe, scrape or soak up in an inert material and put in a container for disposal. Wear proper protective equipment as specified in the protective equipment section.

7. HANDLING AND STORAGE**PRECAUTIONS TO BE TAKEN IN HANDLING AND STORAGE**

Use personal protective equipment. Avoid contact with eyes, skin, and clothing. Keep container closed.

STORAGE

Keep away from heat, sparks and open flame.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION**ENGINEERING CONTROLS**

Eye wash facilities and emergency shower must be available when handling this product.

**RTV630
Silicone Moldmaking Material - Component B****RESPIRATORY PROTECTION**

If exposure limits are exceeded or respiratory irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Supplied air respirators may be required for non-routine or emergency situations. Respiratory protection must be provided in accordance with OSHA regulations (see 29CFR 1910.134).

PROTECTIVE GLOVES

Wear suitable gloves.

EYE AND FACE PROTECTION

Safety glasses with side shields

OTHER PROTECTIVE EQUIPMENT

Wear suitable protective clothing, gloves and eye/face protection.

Exposure Guidelines

Component	CAS-No.	Source	Value
------------------	----------------	---------------	--------------

Absence of values indicates none found

PEL - OSHA Permissible Exposure Limit; TLV - ACGIH Threshold Limit Value; TWA - Time Weighted Average; INTL REL - Internal Recommended Exposure Limit

OSHA revoked the Final Rule Limits of January 19, 1989 in response to the 11th Circuit Court of Appeals decision (AFL-CIO v. OSHA) effective June 30, 1993. See 29 CFR 1910.1000 (58 FR 35338).

9. PHYSICAL AND CHEMICAL PROPERTIES

BOILING POINT (°C):	>300 °C; 572 °F
VAPOR PRESSURE (20 C) (MM HG):	No data available.
VAPOR DENSITY (AIR=1):	No data available.
FREEZING POINT:	No data available.
PHYSICAL STATE:	Liquid
ODOR:	Faint
Color:	Blue
EVAPORATION RATE (BUTYL ACETATE=1):	No data available.
SPECIFIC GRAVITY:	ca. 1.02
DENSITY:	ca. 1.02 g/cm ³
ACID / ALKALINITY (MEQ/G):	No data available.
pH:	Not applicable
SOLUBILITY IN WATER (20 C):	Insoluble
SOLUBILITY IN ORGANIC SOLVENT (STATE SOLVENT):	Soluble in toluene

**RTV630
Silicone Moldmaking Material - Component B**

VOC EXCL. H2O & EXEMPTS (G/L): 5 g/l

10. STABILITY AND REACTIVITY**STABILITY**

Stable

HAZARDOUS POLYMERIZATION.

Hazardous polymerisation does not occur.

HAZARDOUS THERMAL DECOMPOSITION / COMBUSTION PRODUCTS

Flammable hydrogen gas.; Carbon dioxide; Formaldehyde.; Silicon dioxide.; This product contains methylpolysiloxanes which will likely generate formaldehyde at approximately 300 degrees Fahrenheit (150°C) and above, in atmospheres which contain oxygen. Formaldehyde is a skin and respiratory sensitizer, eye and throat irritant, acute toxicant, and has been classified by the National Toxicology Program as a known human carcinogen. A MSDS for formaldehyde is available from Momentive. See Section 11 for additional information on formaldehyde.

INCOMPATIBLE MATERIALS

"Avoid contact with acidic, basic, or oxidizing agents, and""metallic catalysts like tin soaps and noble metals (Pt, Rh,"etc.).

CONDITIONS TO AVOID

Avoid contact with acids and oxidizing substances. Product generates flammable gas on contact with acids, bases or oxidizing substances.

11. TOXICOLOGICAL INFORMATION**ACUTE ORAL**

Remarks: None known.

CARCINOGENICITY

The National Toxicology Program (NTP) classifies formaldehyde as "known to be a human carcinogen" with respect to nasopharyngeal cancer, sinonasal cancer and myeloid leukemia. The International Agency for Research on Cancer (IARC) classifies formaldehyde as "carcinogenic to humans". U.S. OSHA regulates formaldehyde as a potential human carcinogen. See the OSHA Formaldehyde Workplace Standard at 29 CFR 1920.1048 (the "OSHA Standard"). Safe handling and use instructions are provided in this MSDS and in the OSHA Standard. OSHA has identified 0.5 ppm, calculated as an eight-hour time-weighted average ("TWA") concentration, as the "Action Level". Please review and understand the guidance contained in this MSDS, and refer to the OSHA Standard for regulatory requirements that might be applicable to your operation and use. Many studies and other evaluations have been performed concerning formaldehyde's potential to cause cancer. To review some of these studies and for further information go to www.osha.gov; <http://monographs.iarc.fr>; <http://ntp-server.niehs.nih.gov>; <http://epa.gov>; <http://www.nap.edu> and other authoritative websites then

**RTV630
Silicone Moldmaking Material - Component B**

search on formaldehyde.

ACUTE DERMAL

Remarks: None known.

ACUTE INHALATION

Remarks: No data available.

OTHER

None.

MUTAGENICITY

No data available.

12. ECOLOGICAL INFORMATION**CHEMICAL FATE**

No data available.

13. DISPOSAL CONSIDERATIONS**DISPOSAL METHODS**

Disposal should be made in accordance with federal, state and local regulations.

14. TRANSPORT INFORMATION**Further Information:**

This product is not regarded as dangerous goods according to the national and international regulations on the transport of dangerous goods. This product is not prohibited for air shipment by national or international regulations on the transport of dangerous goods. However, as a result of the potential formation of hydrogen gas under certain conditions, Momentive Performance Materials recommends that this product should be shipped using a mode of transportation other than air (IATA-C, IATA-P).

15. REGULATORY INFORMATION

**RTV630
Silicone Moldmaking Material - Component B****Inventories**

Australia Inventory of Chemical Substances (AICS)	y (positive listing)	
EU list of existing chemical substances	y (positive listing)	
Japan Inventory of Existing & New Chemical Substances (ENCS)	n (Negative listing)	
China Inventory of Existing Chemical Substances	y (positive listing)	
Korea Existing Chemicals Inventory (KECI)	y (positive listing)	
Canada DSL Inventory	y (positive listing)	
Canada NDSL Inventory	n (Negative listing)	
Philippines Inventory of Chemicals and Chemical Substances (PICCS)	y (positive listing)	
TSCA list	y (positive listing)	On TSCA Inventory

For inventories that are marked as quantity restricted or special cases, please contact Momentive.

US Regulatory Information

CERCLA Reportable quantity 222717 lbs

<u>PRODUCT COMPOSITION</u>	<u>Chemical</u>	<u>CERCLA Reportable Quantity</u>
Toluene	108-88-3	Reportable quantity: 1,000 LBS

CALIFORNIA PROPOSITION 65

Warning! This product contains a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.

Canadian Regulatory Information**WHMIS CLASSIFICATION**

D2A - Very Toxic Material Causing Other Toxic Effects

16. OTHER INFORMATION**OTHER**

These data are offered in good faith as typical values and not as product specifications. No warranty, either expressed or implied, is made. The recommended industrial hygiene and safe handling procedures are believed to be generally applicable. However, each user should review these recommendations in the specific context of the intended use and determine whether they are appropriate.

RTV630**Silicone Moldmaking Material - Component B**

,C = ceiling limit NEGL = negligible
EST = estimated NF = none found
NA = not applicable UNKN = unknown
NE = none established REC = recommended
ND = none determined V = recommended by vendor
SKN = skin TS = trade secret
R = recommended MST = mist
NT = not tested STEL = short term exposure limit
ppm = parts per million ppb = parts per billion
By-product= reaction by-product, TSCA inventory status not required under 40 CFR part 720.30(h-2).

**RTV630
Silicone Moldmaking Material - Component A****CHRONIC EFFECTS / CARCINOGENICITY**

No data available.

ROUTES OF EXPOSURE

Inhalation

3. COMPOSITION/INFORMATION ON INGREDIENTS**PRODUCT COMPOSITION****CAS-No.****WGT. %****A. HAZARDOUS****B. NON-HAZARDOUS**

polyvinylsiloxane	68083-19-2	30 - 60 %
QUARTZ	14808-60-7	30 - 60 %
Polyalkylalkenylsiloxane	68584-83-8	10 - 30 %
Limestone	471-34-1	1 - 5 %

4. FIRST AID MEASURES**INGESTION**

If swallowed, do NOT induce vomiting. Give a glass of water. Do not give victim anything to drink if he is unconscious. Get medical attention.

SKIN

Wash with soap and water.

INHALATION

If inhaled, remove to fresh air. If not breathing give artificial respiration using a barrier device. If breathing is difficult give oxygen. Get medical attention.

EYES.

In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

NOTE TO PHYSICIAN

Treatment is symptomatic and supportive.

**RTV630
Silicone Moldmaking Material - Component A**

5. FIRE-FIGHTING MEASURES

FLASH POINT: > 100 °C; 212 °F
IGNITION TEMPERATURE: Not applicable
FLAMMABLE LIMITS LEL: No data available.
FLAMMABLE LIMITS UEL: No data available.

SENSITIVITY TO MECHANICAL IMPACT: No

SENSITIVITY TO STATIC DISCHARGE
Sensitivity to static discharge is not expected.

EXTINGUISHING MEDIA
All standard extinguishing agents are suitable.

SPECIAL FIRE FIGHTING PROCEDURES
Firefighters must wear NIOSH/MSHA approved positive pressure self-contained breathing apparatus with full face mask and full protective clothing.

FURTHER INFORMATION
Use standard firefighting procedures and consider the hazards of other involved materials.

6. ACCIDENTAL RELEASE MEASURES

ACTION TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED
Wipe, scrape or soak up in an inert material and put in a container for disposal. Wash walking surfaces with detergent and water to reduce slipping hazard. Wear proper protective equipment as specified in the protective equipment section.

7. HANDLING AND STORAGE

PRECAUTIONS TO BE TAKEN IN HANDLING AND STORAGE
Keep container closed. Avoid contact with eyes, skin, and clothing. Keep out of reach of children.

STORAGE
Keep container closed.

**RTV630
Silicone Moldmaking Material - Component A****8. EXPOSURE CONTROLS/PERSONAL PROTECTION****ENGINEERING CONTROLS**

Eye wash facilities and emergency shower must be available when handling this product.

RESPIRATORY PROTECTION

If exposure limits are exceeded or respiratory irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Supplied air respirators may be required for non-routine or emergency situations. Respiratory protection must be provided in accordance with OSHA regulations (see 29CFR 1910.134).

PROTECTIVE GLOVES

Rubber gloves are recommended.

EYE AND FACE PROTECTION

Safety glasses with side shields

OTHER PROTECTIVE EQUIPMENT

Wear suitable protective clothing and eye/face protection.

Exposure Guidelines

Component	CAS-No.	Source	Value
Ethylbenzene	100-41-4	ACGIH, TWA	20 ppm
Ethylbenzene	100-41-4	OSHA Z1, PEL	100 ppm; 435 mg/m3
Benzene	71-43-2	ACGIH, TWA	0.5 ppm
Benzene	71-43-2	ACGIH, STEL	2.5 ppm
Benzene	71-43-2	ACGIH, SKIN_DES	Can be absorbed through the skin.
Benzene	71-43-2	OSHA Z2, TWA	10 ppm
Benzene	71-43-2	OSHA Z2, Ceiling	25 ppm
Benzene	71-43-2	OSHA Z2, MAX. CONC	50 ppm
Benzene	71-43-2	ACGIH,	Listed.
Benzene	71-43-2	OSHA Z2,	Listed.

Absence of values indicates none found

PEL - OSHA Permissible Exposure Limit; TLV - ACGIH Threshold Limit Value; TWA - Time Weighted Average; INTL REL - Internal Recommended Exposure Limit

OSHA revoked the Final Rule Limits of January 19, 1989 in response to the 11th Circuit Court of Appeals decision (AFL-CIO v. OSHA) effective June 30, 1993. See 29 CFR 1910.1000 (58 FR 35338).

**RTV630
Silicone Moldmaking Material - Component A****9. PHYSICAL AND CHEMICAL PROPERTIES**

BOILING POINT (°C):	>260 °C; 500 °F
VAPOR PRESSURE:	Negligible
VAPOR DENSITY (AIR=1):	1.0
FREEZING POINT:	Not applicable
PHYSICAL STATE:	Liquid
ODOR:	Faint
Color:	Pale yellow
EVAPORATION RATE (BUTYL ACETATE=1):	< 1
SPECIFIC GRAVITY:	ca. 1.28
DENSITY:	ca. 1.28 g/cm ³
ACID / ALKALINITY (MEQ/G):	No data available.
pH:	No data available.
SOLUBILITY IN WATER (20 C):	Insoluble
SOLUBILITY IN ORGANIC SOLVENT (STATE SOLVENT):	Toluene
VOC EXCL. H₂O & EXEMPTS (G/L):	1 g/l

10. STABILITY AND REACTIVITY**STABILITY**

Stable

HAZARDOUS POLYMERIZATION.

Hazardous polymerisation does not occur.

HAZARDOUS THERMAL DECOMPOSITION / COMBUSTION PRODUCTS

Carbon Monoxide.; Carbon dioxide; Silicon dioxide.; Formaldehyde.; This product contains methylpolysiloxanes which can generate formaldehyde at approximately 300 degrees Fahrenheit (150°C) and above, in atmospheres which contain oxygen. Formaldehyde is a skin and respiratory sensitizer, eye and throat irritant, acute toxicant, and potential cancer hazard. A MSDS for formaldehyde is available from Momentive.

INCOMPATIBLE MATERIALS

None known.

CONDITIONS TO AVOID

None known.

**RTV630
Silicone Moldmaking Material - Component A**

11. TOXICOLOGICAL INFORMATION**ACUTE ORAL**

Remarks: No data available.

ACUTE DERMAL

Remarks: No data available.

ACUTE INHALATION

Remarks: No data available.

OTHER

None.

SENSITIZATION

No data available.

SKIN IRRITATION.

No data available.

EYE IRRITATION

No data available.

MUTAGENICITY

No data available.

12. ECOLOGICAL INFORMATION**ECOTOXICITY**

No data available.

DISTRIBUTION

No data available.

CHEMICAL FATE

No data available.

13. DISPOSAL CONSIDERATIONS**DISPOSAL METHODS**

Disposal should be made in accordance with federal, state and local regulations.

**RTV630
Silicone Moldmaking Material - Component A****14. TRANSPORT INFORMATION**

Further Information: This product is not regarded as dangerous goods according to the national and international regulations on the transport of dangerous goods.

15. REGULATORY INFORMATION**Inventories**

Australia Inventory of Chemical Substances (AICS)	y (positive listing)	
EU list of existing chemical substances	y (positive listing)	
Japan Inventory of Existing & New Chemical Substances (ENCS)	y (positive listing)	
China Inventory of Existing Chemical Substances	y (positive listing)	
Korea Existing Chemicals Inventory (KECI)	y (positive listing)	
Canada DSL Inventory	y (positive listing)	
Philippines Inventory of Chemicals and Chemical Substances (PICCS)	y (positive listing)	
TSCA list	y (positive listing)	On TSCA Inventory

For inventories that are marked as quantity restricted or special cases, please contact Momentive.

US Regulatory Information

CERCLA Reportable quantity 133333 lbs

<u>PRODUCT COMPOSITION</u>	Chemical
Xylenes	1330-20-7

CERCLA Reportable Quantity
Reportable quantity: 100 LBS

SARA (311,312) HAZARD CLASS
Acute Health Hazard

SARA (313) CHEMICALS**CALIFORNIA PROPOSITION 65**

Warning! This product contains a chemical known to the State of California to cause cancer, birth defects or other reproductive harm.

100-41-4, Ethylbenzene. 71-43-2, Benzene. 108-88-3, Toluene.

**RTV630
Silicone Moldmaking Material - Component A**

Canadian Regulatory Information**WHMIS CLASSIFICATION**

- This is not a WHMIS controlled product.

16. OTHER INFORMATION**OTHER**

These data are offered in good faith as typical values and not as product specifications. No warranty, either expressed or implied, is made. The recommended industrial hygiene and safe handling procedures are believed to be generally applicable. However, each user should review these recommendations in the specific context of the intended use and determine whether they are appropriate.

,C = ceiling limit NEGL = negligible
EST = estimated NF = none found
NA = not applicable UNKN = unknown
NE = none established REC = recommended
ND = none determined V = recommended by vendor
SKN = skin TS = trade secret
R = recommended MST = mist
NT = not tested STEL = short term exposure limit
ppm = parts per million ppb = parts per billion
By-product= reaction by-product, TSCA inventory status not required under 40 CFR part 720.30(h-2).