


Cree[®] XLamp[®] ML-E LEDs





FEATURES



The XLamp ML-E LED brings high performance and a smooth look to a wide range of lighting applications, including linear lighting, LED light bulbs, fluorescent retrofits and retail-display lighting.

•	Available in white (2600 K to
	8300 K CCT), 80-, 85- and
	90-CRI minimum

- Available in royal blue, blue, green, amber and red
- Available in parallel and series
 Vf configurations for white and color
- ANSI-compatible sub-bins
- Maximum drive current: 500 mA for parallel white, 167 mA for series white, 350 mA for parallel royal blue, blue, green and red, 250 mA for parallel amber, 120 mA for series blue and green, 65 mA for series amber, 88 mA for series red
- 120° viewing angle for white,
 125° viewing angle for color
- Uniform chromaticity profile
- Electrically neutral thermal path
- RoHS- and REACh-compliant
- UL-recognized component (E349212)





TABLE OF CONTENTS

Characteristics 2
Flux Characteristics 3
Relative Spectral Power
Distribution
Relative Luminous Flux vs.
Junction Temperature 8
Relative Radiant Flux vs. Junction
Temperature 9
Electrical Characteristics10
Relative Luminous Flux vs.
Current12
Relative Radiant Flux vs. Current14
Typical Spatial Distribution14
Thermal Design16
Reflow Soldering Characteristics 21
Notes22
Mechanical Dimensions24
Tape and Reel25
Packaging26



CHARACTERISTICS $(T_j = 25 \text{ °C})$

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point - white, royal blue, blue	°C/W		11	
Thermal resistance, junction to solder point - green, red	°C/W		15	
Thermal resistance, junction to solder point - amber	°C/W		24	
Viewing angle (FWHM) - white	degrees		120	
Viewing angle (FWHM) - royal blue, blue, green, amber, red	degrees		125	
Temperature coefficient of voltage - parallel - white, royal blue, blue	mV/°C		-3.3	
Temperature coefficient of voltage - series - white, blue	mV/°C		-10	
Temperature coefficient of voltage - parallel - green	mV/°C		-4	
Temperature coefficient of voltage - series - green	mV/°C		-11	
Temperature coefficient of voltage - parallel - amber	mV/°C		-1	
Temperature coefficient of voltage - series - amber	mV/°C		-3.2	
Temperature coefficient of voltage - parallel - red	mV/°C		-1.8	
Temperature coefficient of voltage - series - red	mV/°C		-5.4	
ESD withstand voltage (HBM per Mil-Std-883D) - white, royal blue, blue, green	V			8000
ESD classification (HBM per Mil-Std-883D) - amber, red			Class 2	
DC forward current - parallel - white	mA			500
DC forward current - series - white	mA			167
DC forward current - parallel - royal blue, blue, green, red	mA			350
DC forward current - series - blue, green	mA			120
DC forward current - parallel - amber	mA			250
DC forward current - series - amber	mA			65
DC forward current - series - red	mA			88
Reverse voltage	V			-5
Forward voltage (@ 150 mA) - parallel - white	V		3.2	3.4
Forward voltage (@ 50 mA) - series - white	V		9.6	10.2
Forward voltage (@ 150 mA) - parallel - royal blue, blue	V		3.2	
Forward voltage (@ 50 mA) - series - blue	V		9.6	
Forward voltage (@ 150 mA) - parallel - green	V		3.3	
Forward voltage (@ 50 mA) - series - green	V		9.9	
Forward voltage (@ 150 mA) - parallel - amber, red	V		2.4	
Forward voltage (@ 37.5 mA) - series - amber, red	V		9.6	
LED junction temperature	°C			150



FLUX CHARACTERISTICS - PARALLEL WHITE (T, = 25 °C)

The following table provides several base order codes for XLamp ML-E LEDs. It is important to note that the base order codes listed here are a subset of the total available order codes for the product family. For more order codes, as well as a complete description of the order-code nomenclature, please consult the XLamp ML-E LED Binning and Labeling document.

Color	CCT Range		Base Order Codes Minimum Luminous Flux (lm) @ 150 mA		Calculated Minimum Luminous Flux (lm)*		Order Code				
	Min.	Max.	Group	Flux (lm)	350 mA	500 mA					
Cool White	5000 K	8300 K	N2	51.7	104.8	132.9	MLEAWT-A1-0000-000451				
Cool Wille	5000 K	0300 K	М3	45.7	92.6	117.4	MLEAWT-A1-0000-000351				
80-CRI	6000 K	7000 K	М3	45.7	92.6	117.4	MLEAWT-H1-0000-0003E1				
Cool White	4750 K	5250 K	М3	45.7	92.6	117.4	MLEAWT-H1-0000-0003E3				
	3700 K	2700 1/	2700 K	2700 K	2700 1/ 420/	4300 K	М3	45.7	92.6	117.4	MLEAWT-A1-0000-0003E5
Warm White		4300 K	M2	39.8	80.7	102.3	MLEAWT-A1-0000-0002E5				
warm winte	2000 1/	3200 K	M2	39.8	80.7	102.3	MLEAWT-A1-0000-0002E7				
	2800 K		K3	35.2	71.4	90.5	MLEAWT-A1-0000-0001E7				
80-CRI	3700 K	4300 K	M2	39.8	80.7	102.3	MLEAWT-H1-0000-0002E5				
Warm White	2800 K	3200 K	K3	35.2	71.4	90.5	MLEAWT-H1-0000-0001E7				
85-CRI Warm White	2800 K	3200 K	K3	35.2	71.4	90.5	MLEAWT-P1-0000-0001E7				
90-CRI Warm White	2800 K	3200 K	K2	30.6	62	78.6	MLEAWT-U1-0000-0000E7				

Notes:

- Cree maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and ± 2 on CRI measurements.
- Typical CRI for Cool White (4300 K 8300 K CCT) is 75.
- Typical CRI for Warm White (2600 K 4300 K CCT) is 80.
- Minimum CRI for 80-CRI White is 80.
- Minimum CRI for 85-CRI White is 85.
- Minimum CRI for 90-CRI White is 90
- * Calculated flux values are for reference only.



FLUX CHARACTERISTICS - SERIES WHITE $(T_1 = 25 \text{ °C})$

The following table provides several base order codes for XLamp ML-E LEDs. It is important to note that the base order codes listed here are a subset of the total available order codes for the product family. For more order codes, as well as a complete description of the order-code nomenclature, please consult the XLamp ML-E LED Binning and Labeling document.

Color	CCT Range		Base Order Codes Minimum Luminous Flux (lm) @ 50 mA		Calculated Minimum Luminous Flux (lm)*		Order Code			
	Min.	Max.	Group	Flux (lm)	117 mA	166 mA				
Cool White	5000 K	8300 K	N2	51.7	104.8	132.9	MLESWT-A1-0000-000451			
Cool white	5000 K	6300 K	М3	45.7	92.6	117.4	MLESWT-A1-0000-000351			
80-CRI	6000 K	7000 K	М3	45.7	92.6	117.4	MLESWT-H1-0000-0003E1			
Cool White	4750 K	5250 K	М3	45.7	92.6	117.4	MLESWT-H1-0000-0003E3			
	3700 K	2700 V	3700 K	2700 K	4300 K	М3	45.7	92.6	117.4	MLESWT-A1-0000-0003E5
Warm White		4300 K	M2	39.8	80.7	102.3	MLESWT-A1-0000-0002E5			
warm winte	2000 K	2800 K 3200 K	M2	39.8	80.7	102.3	MLESWT-A1-0000-0002E7			
	2000 K		К3	35.2	71.4	90.5	MLESWT-A1-0000-0001E7			
80-CRI	3700 K	4300 K	M2	39.8	80.7	102.3	MLESWT-H1-0000-0002E5			
Warm White	2800 K	3200 K	K3	35.2	71.4	90.5	MLESWT-H1-0000-0001E7			
85-CRI Warm White	2800 K	3200 K	K3	35.2	71.4	90.5	MLESWT-P1-0000-0001E7			
90-CRI Warm White	2800 K	3200 K	K2	30.6	62	78.6	MLESWT-U1-0000-0000E7			

Notes:

- Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and ±2 on CRI measurements.
- Typical CRI for Cool White (4300 K 8300 K CCT) is 75.
- Typical CRI for Warm White (2600 K 4300 K CCT) is 80.
- Minimum CRI for 80-CRI White is 80.
- Minimum CRI for 85-CRI White is 85.
- Minimum CRI for 90-CRI White is 90.
- Calculated flux values are for reference only.



FLUX CHARACTERISTICS - PARALLEL COLOR (T_J = 25 °C)

The following table provides several base order codes for XLamp ML-E color LEDs. It is important to note that the base order codes listed here are a subset of the total available order codes for the product family. For more order codes, as well as a complete description of the order-code nomenclature, please consult the XLamp ML Family Binning and Labeling document.

	Color	Domi	nant Wav	elength F	Range		der Codes n Radiant		
		Min.		Max.		Flux (mW) @ 150 mA		Order Code	
		Group	DWL (nm)	Group	DWL (nm)	Group	Flux (mW)		
	Royal Blue	D3	450	D5	465	10	175	MLEROY-A1-0000-000501	

	Domi	nant Wav	elength F	Range	Base Order Codes Minimum			
Color	Min.		Max.		Luminous Flux (lm) @ 150 mA		Order Code	
	Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)		
Blue	B3 465	D2 465	D.C.	405	G0	13.9	MLEBLU-A1-0000-000U01	
blue		В6	485	F0	10.7	MLEBLU-A1-0000-000T01		

	Domi	nant Wav	elength F	Range		Order Minimum		
Color	Min.		Max.		Luminous Flux (lm) @ 150 mA		Order Code	
	Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)		
			G4	64 535	K3	35.2	MLEGRN-A1-0000-000101	
Green	G2 520	520			K2	30.6	MLEGRN-A1-0000-000001	
				J3	26.8	MLEGRN-A1-0000-000X01		

	Color	Domi	nant Wav	elength F	Range	Base Order Codes Minimum			
Col		Min.		Max.		Luminous Flux (lm) @ 150 mA		Order Code	
		Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)		
A m	hom	A2 58	42 505	585 A3	595	J3	26.8	MLEAMB-A1-0000-000X01	
Ami	ber		363			J2	23.5	MLEAMB-A1-0000-000W01	

	Domi	nant Wav	elength F	Range	Base Order Codes Minimum			
Color	Min.		Max.		Luminous Flux (lm) @ 150 mA		Order Code	
	Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)		
Red	R2	620	D.2	כח	630	J2	23.5	MLERED-A1-0000-000W01
Reu	R2 620	R3	030	H0	18.1	MLERED-A1-0000-000V01		

Note:

Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements, ±2 on CRI measurements and ± 1 nm on dominant wavelength measurements.



FLUX CHARACTERISTICS - SERIES COLOR (T_j = 25 °C)

The following table provides several base order codes for XLamp ML-E color LEDs. It is important to note that the base order codes listed here are a subset of the total available order codes for the product family. For more order codes, as well as a complete description of the order-code nomenclature, please consult the XLamp ML Family Binning and Labeling document.

	Domi	nant Wav	elength F	Range	Base Order Codes Minimum			
Color	Min.		Max.		Luminous Flux (Im) @ 50 mA		Order Code	
	Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)		
Blue	D2 4	B3 465 B6	D.C	D6 40E	G0	13.9	MLESBL-A1-0000-000U01	
blue	DO		485	F0	10.7	MLESBL-A1-0000-000T01		

Color	Domi	nant Wav	elength F	Range		Order Minimum			
	Min.		Max.		Luminous Flux (Im) @ 50 mA		Order Code		
	Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)			
						K3	35.2	MLESGN-A1-0000-000101	
Green	G2	520	G4	535	K2	30.6	MLESGN-A1-0000-000001		
							J3	26.8	MLESGN-A1-0000-000X01

Color	Dominant Wavelength Range				Base Order Codes Minimum			
	Min.		Max.		Luminous Flux (Im) @ 37.5 mA		Order Code	
	Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)		
Amber	A2 5	585	A3	595	J3	26.8	MLESAM-A1-0000-000X01	
Amber		363	363 A3	393	J2	23.5	MLESAM-A1-0000-000W01	


Color	Dominant Wavelength Range				Base Order Codes Minimum			
	Min.		Max.		Luminous Flux (Im) @ 37.5 mA		Order Code	
	Group	DWL (nm)	Group	DWL (nm)	Group	Flux (lm)		
Red	D.O.	R2 620 R3	D.S.	620	J2	23.5	MLESRD-A1-0000-000W01	
Kea	KZ		K3	630	H0	18.1	MLESRD-A1-0000-000V01	

Note


• Cree maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements, ±2 on CRI measurements and ± 1 nm on dominant wavelength measurements.



RELATIVE SPECTRAL POWER DISTRIBUTION - WHITE




RELATIVE SPECTRAL POWER DISTRIBUTION - COLOR






RELATIVE LUMINOUS FLUX VS. JUNCTION TEMPERATURE - WHITE (PARALLEL: $I_F = 150$ mA, SERIES: $I_F = 50$ mA)




RELATIVE LUMINOUS FLUX VS. JUNCTION TEMPERATURE - PARALLEL: BLUE, GREEN, AMBER, RED ($I_F = 150 \text{ mA}$), SERIES: BLUE, GREEN ($I_F = 50 \text{ mA}$) AMBER, RED ($I_F = 37.5 \text{ mA}$)






RELATIVE RADIANT FLUX VS. JUNCTION TEMPERATURE - PARALLEL ROYAL BLUE ($I_F = 150 \text{ mA}$)






ELECTRICAL CHARACTERISTICS - PARALLEL WHITE (T_j = 25 °C)




ELECTRICAL CHARACTERISTICS - SERIES WHITE (T₁ = 25 °C)






ELECTRICAL CHARACTERISTICS - PARALLEL COLOR (T₁ = 25 °C)




ELECTRICAL CHARACTERISTICS - SERIES COLOR (T, = 25 °C)






RELATIVE LUMINOUS FLUX VS. CURRENT - PARALLEL WHITE ($T_1 = 25$ °C)



Forward Current (mA)


RELATIVE LUMINOUS FLUX VS. CURRENT - SERIES WHITE $(T_1 = 25 \text{ °C})$




Forward Current (mA)



RELATIVE LUMINOUS FLUX VS. CURRENT - PARALLEL BLUE, GREEN, AMBER, RED ($T_1 = 25$ °C)




RELATIVE LUMINOUS FLUX VS. CURRENT - SERIES BLUE, GREEN, AMBER, RED ($T_1 = 25$ °C)






RELATIVE RADIANT FLUX VS. CURRENT - PARALLEL ROYAL BLUE ($T_1 = 25$ °C)




TYPICAL SPATIAL DISTRIBUTION - WHITE






TYPICAL SPATIAL DISTRIBUTION - ROYAL BLUE, BLUE, GREEN




TYPICAL SPATIAL DISTRIBUTION - AMBER, RED






THERMAL DESIGN - PARALLEL WHITE

The maximum forward current is determined by the thermal resistance between the LED junction and ambient. It is crucial for the end product to be designed in a manner that minimizes the thermal resistance from the solder point to ambient in order to optimize lamp life and optical characteristics.




THERMAL DESIGN - SERIES WHITE






THERMAL DESIGN - PARALLEL ROYAL BLUE, BLUE




THERMAL DESIGN - SERIES BLUE






THERMAL DESIGN - PARALLEL GREEN




THERMAL DESIGN - SERIES GREEN






THERMAL DESIGN - PARALLEL AMBER




THERMAL DESIGN - SERIES AMBER






THERMAL DESIGN - PARALLEL RED



THERMAL DESIGN - SERIES RED






REFLOW SOLDERING CHARACTERISTICS

In testing, Cree has found XLamp ML-E LEDs to be compatible with JEDEC J-STD-020C, using the parameters listed below. As a general guideline, Cree recommends that users follow the recommended soldering profile provided by the manufacturer of the solder paste used.

Note that this general guideline may not apply to all PCB designs and configurations of reflow soldering equipment.



Profile Feature	Lead-Based Solder	Lead-Free Solder	
Average Ramp-Up Rate (Ts _{max} to Tp)	3 °C/second max.	3 °C/second max.	
Preheat: Temperature Min (Ts _{min})	100 °C	150 °C	
Preheat: Temperature Max (Ts _{max})	150 °C	200 °C	
Preheat: Time (ts _{min} to ts _{max})	60-120 seconds	60-180 seconds	
Time Maintained Above: Temperature (T _L)	183 °C	217 °C	
Time Maintained Above: Time (t _L)	60-150 seconds	60-150 seconds	
Peak/Classification Temperature (Tp)	215 °C	260 °C	
Time Within 5 °C of Actual Peak Temperature (tp)	10-30 seconds	20-40 seconds	
Ramp-Down Rate	6 °C/second max.	6 °C/second max.	
Time 25 °C to Peak Temperature	6 minutes max.	8 minutes max.	

Note: All temperatures refer to topside of the package, measured on the package body surface.

Note: While the high reflow temperatures (above) have been approved, Cree's best practice guideline for reflow is to use as low a temperature as possible during the reflow soldering process for these LEDs.



NOTES

Lumen Maintenance Projections

Cree now uses standardized IES LM-80-08 and TM-21-11 methods for collecting long-term data and extrapolating LED lumen maintenance. For information on the specific LM-80 data sets available for this LED, refer to the public LM-80 results document at www.cree.com/xlamp_app_notes/LM80_results.

Please read the XLamp Long-Term Lumen Maintenance application note at www.cree.com/xlamp_app_notes/lumen_maintenance for more details on Cree's lumen maintenance testing and forecasting. Please read the XLamp Thermal Management application note at www.cree.com/xlamp_app_notes/thermal_management for details on how thermal design, ambient temperature, and drive current affect the LED junction temperature.

Moisture Sensitivity

XLamp ML-E LEDs are shipped in sealed, moisture-barrier bags (MBB) designed for long shelf life. If XLamp ML-E LEDs are exposed to moist environments after opening the MBB packaging but before soldering, damage to the LED may occur during the soldering operation. The derating table at right defines the maximum exposure time (in days) for an XLamp ML-E LED in the listed humidity and temperature conditions.

Town	Maximum Percent Relative Humidity								
Temp.	30%	40%	50%	60%	70%	80%	90%		
35 °C	-	-	-	17	1	.5	.5		
30 °C	-	-	-	28	1	1	1		
25 °C	-	-	-	-	2	1	1		
20 °C	-	-	-	-	2	1	1		

LEDs with exposure time longer than the time specified below must be baked according to the baking conditions listed below.

Cree recommends keeping XLamp LEDs in their sealed moisture-barrier packaging until immediately prior to use. Cree also recommends returning any unused LEDs to the resealable moisture-barrier bag and closing the bag immediately after use.

Baking Conditions

It is not necessary to bake all XLamp ML-E LEDs. Only the LEDs that meet all of the following criteria must be baked:

- 1. LEDs that have been removed from the original MBB packaging.
- 2. LEDs that have been exposed to a humid environment longer than listed in the Moisture Sensitivity section above.
- 3. LEDs that have not been soldered.

LEDs should be baked at 70 °C for 24 hours. LEDs may be baked on the original reels. Remove LEDs from MBB packaging before baking. Do not bake parts at temperatures higher than 70 °C. This baking operation resets the exposure time as defined in the Moisture Sensitivity section above.



Storage Conditions

XLamp ML-E LEDs that have been removed from the original MBB packaging but not soldered should be stored in one of the following ways:

- Store the parts in a rigid metal container with a tight-fitting lid. Verify that the storage temperature is <30 °C, and place fresh desiccant and an RH indicator in the container to verify that the RH is no greater than 60%.
- Store the parts in a dry, nitrogen-purged cabinet or container that actively maintains the temperature at <30° and the RH at no greater than 60%.
- For short-term store only: LEDs can be resealed in the original MBB bag soon after opening. Fresh desiccant may be needed. Use the included humidity indicator card to verify <60% RH.

If an environment of <60% RH is not available for storage, XLamp ML-E LEDs should be baked (described above) before reflow soldering.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree representative or from the Product Documentation sections of www.cree.com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Cree representative to insure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

UL Recognized Component

Level 4 enclosure consideration. The LED package or a portion thereof has been investigated as a fire and electrical enclosure per ANSI/UL 8750.


Vision Advisory Claim

WARNING: Do not look at an exposed lamp in operation. Eye injury can result. See LED Eye Safety at www.cree.com/xlamp_app_notes/led_eye_safety.



MECHANICAL DIMENSIONS ($T_A = 25$ °C)

All measurements are $\pm .13$ mm unless otherwise indicated.







TAPE AND REEL

All Cree carrier tapes conform to EIA-481D, Automated Component Handling Systems Standard.

All dimensions in mm.







PACKAGING

Label with Cree Bin Code, Qty, Reel ID

