

# LXML-PWC1-0100 Luxeon Rebel Starboard LED



Opulent Part Number: REBEL-STAR-CW100

**Opulent Starboard: MCPCB** 

Luxeon Rebel LED: LXML-PWC1-0100



#### **Features**

- Excellent thermal conductivity
- Excellent insulating ability
- Excellent DimensionalStability
- Excellent Mechanical Strength
- Lower heat expansibility
- Lower operating temperature
- Increase power density
- Reduce the number of interconnects
- Extend the life of dies

# OP REBEL STAR

\*\*\*\*\*

OP REBEL STAR

ALUMINUM CLAD PRINTED

CIRCUIT BOARD FOR

LUXEON REBEL ALLOWS

OPTIMUM HEAT

DISSIPATION.





This is a custom MCPCB structure that further enhances heat dissipation and thus enabling the LED to last according to its life time.


Higher thermal conductive MCPCB is also available with our special enhanced capabilities.

### **CONSTRUCTION OF MCPCB**

The structure of the aluminum material includes copper layer, dielectric layer laminated together with aluminum base layer. Below appends summary of available range of material:

| Aluminum | Aluminum  | Copper    | Dielectric |  |
|----------|-----------|-----------|------------|--|
| Type     | Thickness | Thickness | Thickness  |  |
| AL 5052  | 1.5 mm    | 1 oz      | 0.100mm    |  |

### PANEL DRAWING



#### MATERIAL DATASHEET

#### Material Datasheet - OPT111.01.Al5215.4.0018 **Treatment** Value Unit Condition **Thermal Properties** Thermal Conductivity 1.8 W/m-k (Dielectric layer) Thermal Resistance °C-in²/W 0.086 (Dielectric layer) **Maximum Operating Temperature UL 746** 125 $^{\circ}C$ °C Glass Transition Temp (Tg) DSC 130 21.5 < Tg x10<sup>-6</sup>/°C Coefficient of Thermal Expansion (CTE) 22.0 > Tg **Electrical Properties** 4.2 Dielectric constant 1kHz/1MHz **Dissipation Factor** 1kHz/1MHz 0.02 1×10<sup>8</sup> Volume Resistivity C-96/40/90 $M\Omega \cdot cm$ **Surface Resistivity** C-96/40/90 1×10<sup>7</sup> МΩ Dielectric Breakdown Voltage Α 30 KV/mm **Mechanical Properties** Dielectric Thickness Α 100 μm Peel Strength Α 1.05 N/mm **Chemical Properties** D-24/23 0.09 % Water absorption **Ratings and Durability UL Flammablility** 94 V-0 Comparative Tracking Index IEC60112 600 10 sec @ 288 °C, Thermal stress Pass 3 cycles Time to delamination 5min @ 260 °C Pass

<sup>\*</sup> The data is based on typical values of standard production and should be considered as general information. Our company reserves the right for future changes. It is the responsibility of the user to ensure that the product complies with his requirements.



### PRODUCT SPECIFICATIONS

#### **OP REBEL STAR MCPCB**

Aluminum Type: AL5052

Aluminum Thickness: 1.5mm

Copper Thickness: 1oz


Dielectric Thickness: 0.1mm

Unit Size: 21.38 x 19.92mm (±0.1mm)

Panel Size: 136.9 x 91.67mm (24pcs/pnl)

Finishing: OSP

Solder Mask: Glossy Black



#### **SOLDER PASTE**

Type: Leadfree SAC 305 paste, grade 3 or above

Lumileds Internal: Alpha Metal OM325 grade 4

Alternative: Alpha Metal OM338 grade 3

#### **PACKAGING**

One carton consists of 10 internal white boxes. Each white box consists of 3 trays. Each tray consists of 48 pieces.

Type of tray: Individual slot for each OP Rebel Star

Cavity per tray: 48 pcs

Dimension of tray: 44.3cm x 17.25cm x 2.3cm

Internal White Box: contains 3 trays with 1 cover tray (equivalent to 144pcs of OP Rebel)

Dimension of I.W.B: 44.8cm x 17.7cm x 5.5cm

Carton box: contains 10 white boxes (equivalent to 1440pcs of OP Rebel Star)

Dimension of carton: 45.5cm x 36.4cm x 28.5cm



### **ABOUT OPULENT**

Opulent (Asia)

Email: sales@opulent-group.com


Singapore **2**: +65 67498188 (Head Office)

eadquartered in Singapore, Opulent has more than 20 years experience in the manufacturing of conventional printed circuit boards (PCBs). Embarking for an international presence, Opulent has set up sales and marketing support in China, Hong Kong, Germany, Italy, United Kingdom and Malaysia.

Through innovation and R&D, Opulent created metal-clad PCBs (MCPCB) and is currently a leading designer and manufacturer of thermal solutions. Our products and works are guided by a customer centric approach that empowers us to provide value added solutions from design to assembly.

Our customers are well-known international brands whom have come to trust Opulent for our innovation, our knowledge and our commitment to attain customer satisfaction.





LUXEON Rebel General Purpose White Portfolio

High flux and color stability

Technical Datasheet DS64





# LUXEON Rebel

### General Purpose White Portfolio

Cool-white/Neutral white

#### Introduction

The LUXEON® Rebel General Purpose White Portfolio LEDs in this datasheet are ideal for all lighting and illumination applications. These flux differentiated parts, like all other LUXEON Rebel LEDs, provide the industry's best lumen maintenance, superior reliability and quality white light that make them the most widely used power LEDs today. Using the information in this document you can start designing applications to your unique specifications.

#### LUXEON Rebel General Purpose White LEDs

- Deliver more usable light and higher flux density
- · Optimize applications to reduce size and cost
- Tightly pack the LEDs for mixing
- Engineer more robust applications
- Utilize standard FR4 PCB technology
- Simplify manufacturing through the use of surface mount technology
- Recognized under the Component Recognition Program of Underwriters Laboratories Inc. UL listing E327436.



# Table of Contents

| General Product Information                           | 3  |
|---|----|
| Product Nomenclature                                  | 3  |
| Average Lumen Maintenance Characteristics             | 3  |
| Environmental Compliance                              | 3  |
| Luminous Flux Characteristics                         | 4  |
| Flux Performance, Binning, and Supportability         | 4  |
| Optical Characteristics                               | 5  |
| Electrical Characteristics                            | 6  |
| Absolute Maximum Ratings                              | 7  |
| JEDEC Moisture Sensitivity                            | 7  |
| Reflow Soldering Characteristics                      | 8  |
| Mechanical Dimensions                                 | 9  |
| Pad Configuration                                     | 10 |
| Solder Pad Design                                     | 10 |
| Wavelength Characteristics                            | 11 |
| Typical Light Output Characteristics over Temperature | 12 |
| Typical Forward Current Characteristics               | 13 |
| Typical Relative Luminous Flux                        | 14 |
| Current Derating Curves                               | 15 |
| Typical Radiation Patterns                            | 17 |
| Emitter Pocket Tape Packaging                         | 18 |
| Emitter Reel Packaging                                | 19 |
| Product Binning and Labeling                          | 20 |
| Luminous Flux Bins                                    | 21 |
| Cool-White Bin Structure                              | 22 |
| Neutral-White Bin Structure                           | 24 |
| Forward Voltage Bins                                  | 25 |

## General Product Information

### **Product Nomenclature**

LUXEON Rebel is tested and binned at 350 mA, with current pulse duration of 20 ms. All characteristic charts where the thermal pad is kept at constant temperature (25°C typically) are measured with current pulse duration of 20 ms. Under these conditions, junction temperature and thermal pad temperature are the same.

The part number designation is explained as follows:

LXML-ABCD-EFGH

#### Where:

A — designates radiation pattern (value P for Lambertian)

B — designates color (W = White)

C — designates tint variant (C = Cool-White or N = Neutral-White)

D — designates test current (value I for 350 mA)

E — reserved for future product offerings

FGH — minimum luminous flux (lm)

Therefore products tested and binned at 350 mA follow the part numbering scheme:

LXML-PWxI-0xxx

### Average Lumen Maintenance Characteristics

Lumen maintenance for solid-state lighting devices (LEDs) is typically defined in terms of the percentage of initial light output remaining after a specified period of time. Philips Lumileds projects that LUXEON Rebel products will deliver, on average, 70% lumen maintenance (L70) at 50,000 hours of operation at a forward current of up to 700 mA. This projection is based on constant current operation with junction temperature maintained at or below I35°C. This performance is based on independent test data, Philips Lumileds historical data from tests run on similar material systems, and internal LUXEON reliability testing. Observation of design limits included in this data sheet is required in order to achieve this projected lumen maintenance.

### **Environmental Compliance**

Philips Lumileds is committed to providing environmentally friendly products to the solid-state lighting market. LUXEON Rebel is compliant to the European Union directives on the restriction of hazardous substances in electronic equipment, namely the REACH and RoHS directives. Philips Lumileds will not intentionally add the following restricted materials to the LUXEON Rebel: lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE).

### Luminous Flux Characteristics

# Luminous Flux Characteristics for LUXEON Rebel, Thermal Pad Temperature=25°C

Table 1.


|                  |                | Table                      |         |                     |         |
|------------------|----------------|----------------------------|---------|---------------------|---------|
|                  |                | Performance at Test Curren | t       | Typical Perf        |         |
|                  |                |                            |         | at Indicated        |         |
| Color            | Part Number    | Minimum Luminous           | Test    | Typical Luminous    | Drive   |
|                  |                | Flux (Im)                  | Current | Flux (lm)           | Current |
|                  |                | $\Phi_{v}^{[i]}$           | (mA)    | $\Phi_{V}^{^{[2]}}$ | (mA)    |
|                  | LXML-PWC1-0090 | 90                         | 350     | 160                 | 700     |
| C 1) A / L ' L   | LXML-PWC1-0100 | 100                        | 350     | 180                 | 700     |
| Cool White       | LXML-PWCI-0110 | 110                        | 350     | 200                 | 700     |
|                  | LXML-PWC1-0120 | 120                        | 350     | 220                 | 700     |
|                  |                |                            |         |                     |         |
| ·                | LXML-PWN1-0090 | 90                         | 350     | 160                 | 700     |
| Neutral-White    | LXML-PWN1-0100 | 100                        | 350     | 180                 | 700     |
| i veutrai-vvnite | LXML-PWN1-0110 | 110                        | 350     | 200                 | 700     |
|                  | LXML-PWN1-0120 | 120                        | 350     | 220                 | 700     |

#### Notes for Table 1:

- 1. Minimum luminous flux performance guaranteed within published operating conditions. Philips Lumileds maintains a tolerance of ± 6.5% on flux measurements.
- 2. Typical luminous flux performance when device is operated within published operating conditions.

### Flux Performance, Binning, and Supportability

LEDs are produced with semiconductor technology that is subject to process variation, yielding a range of flux performance that is approximately Gaussian in nature. In order to provide customers with fine granularity within the overall flux distribution, Philips Lumileds separates LEDs into fixed, easy to design with, minimum luminous flux bins. To verify supportability of parts chosen for your application design, please consult your Philips Lumileds representative.



# Optical Characteristics

# Lambertian LUXEON Rebel at Test Current [1] Thermal Pad Temperature = 25°C

Table 2.

|                | Colo  | r Temperatur<br>CCT | e <sup>[2],[3]</sup> | Typical Total Included Angle [5] (degrees) | Typical Viewing Angle [6] (degrees) |  |
|----------------|-------|---------------------|----------------------|--|-------------------------------------|--|
| Color [6], [7] | Min.  | Тур.                | Max.                 | $\theta_{0.90V}^{[4]}$                     | 2θ 1/2                              |  |
| Cool-White     | 4500K | 6500K               | 10,000K              | 160  | 120                                 |  |
| Neutral-White  | 3500K | 4100K               | 4500K                | 160  | 120                                 |  |

#### Notes for Table 2:

- 1. Test current is 350 mA for all LXML-PWx1-0xxx products.
- 2. CCT ±5% tester tolerance.
- 3. Typical CRI (Color Rendering Index) for cool-white and neutral-white is 70.
- 4. Total angle at which 90% of total luminous flux is captured.
- 5. Viewing angle is the off axis angle from lamp centerline where the luminous intensity is ½ of the peak value.
- 6. All white products are built with Indium Gallium Nitride (InGaN).
- 7. Cool-white and neutral-white power light sources represented here are IEC825 class 2 for eye safety.

### Electrical Characteristics

# Electrical Characteristics at 350 mA for LUXEON Rebel, Part Numbers LXML-PWxI-0xxx, Thermal Pad Temperature = 25°C

Table 3.

|               |      |                 |                  | Typical Temperature                         | Typical Thermal    |
|---------------|------|-----------------|------------------|---|--------------------|
|               |      |                 |                  | Coefficient of                              | Resistance         |
|               | Fo   | rward Voltage V | [ <sup>1</sup> ] | Forward Voltage [2]                         | Junction to        |
|               |      | (V)             | •                | (mV/°C)                                     | Thermal Pad (°C/W) |
| Color         | Min. | Тур.            | Max.             | $\Delta V_{_{ m f}}$ / $\Delta T_{_{ m J}}$ | $R 	heta_{J-C}$    |
| Cool-White    | 2.55 | 3.00            | 3.99             | -2.0 to -4.0                                | 10                 |
| Neutral-White | 2.55 | 3.00            | 3.99             | -2.0 to -4.0                                | 10                 |

#### Notes for Table 3:

- 1. Philips Lumileds maintains a tolerance of  $\pm 0.06 \text{V}$  on forward voltage measurements.
- 2. Measured between  $25^{\circ}C = T_{l} = 110^{\circ}C$  at  $I_{r} = 350$  mA.

# Typical Electrical Characteristics at 700 mA for LUXEON Rebel, Part Numbers LXML-PWxI-0xxx, Thermal Pad Temperature = 25°C [2]

Table 4.

|               | Typical Forward Voltage V <sub>f</sub> [1] |
|---------------|--|
| Color         | (V)  |
| Cool-White    | 3.20                                       |
| Neutral-White | 3.20                                       |

#### Notes for Table 4:

- 1. Philips Lumileds maintains a tolerance of ±0.06V on forward voltage measurements.
- 2. Measured between  $25^{\circ}C = T_{\parallel} = 110^{\circ}C$  at  $I_{f} = 700$  mA.

## Absolute Maximum Ratings

Table 5.

| Parameter                            | Cool-White/Neutral-White                    |  |
|--------------------------------------|---|--|
| DC Forward Current (mA)              | 1000  |  |
| Peak Pulsed Forward Current (mA)     | 1000  |  |
| Average Forward Current (mA)         | 1000  |  |
| ESD Sensitivity                      | < 8000V Human Body Model (HBM)              |  |
|                                      | Class 2 JESD22-A114-B                       |  |
|                                      | < 400V Machine Model (MM)                   |  |
|                                      | Class 2 JESD22-A115-B                       |  |
| LED Junction Temperature [1]         | 150°C                                       |  |
| Operating Case Temperature at 350 mA | -40°C - 135°C                               |  |
| Storage Temperature                  | -40°C - 135°C                               |  |
| Soldering Temperature                | JEDEC 020c 260°C                            |  |
| Allowable Reflow Cycles              | 3   |  |
| Autoclave Conditions                 | 121°C at 2 ATM                              |  |
|                                      | 100% Relative Humidity for 96 Hours Maximum |  |
| Reverse Voltage (Vr)                 | See Note 2                                  |  |

#### Notes for Table 5:

- 1. Proper current derating must be observed to maintain junction temperature below the maximum.
- 2. LUXEON Rebel LEDs are not designed to be driven in reverse bias.

## JEDEC Moisture Sensitivity

Table 6.

|       |           |            | Soak Requ | iirements  |  |
|-------|-----------|------------|-----------|------------|--|
| Level | Floo      | r Life     | Stand     | ard        |  |
|       | Time      | Conditions | Time      | Conditions |  |
| 1     | unlimited | ≤ 30°C /   | 168h      | 85°C / 85% |  |
|       |           | 85% RH     | + 5 / -0  | RH         |  |

# Reflow Soldering Characteristics




Table 7

| Table 7.   |                    |  |
|--|--------------------|--|
| Profile Feature  | Lead Free Assembly |  |
| Average Ramp-Up Rate $(Ts_{max} to T_p)$                     | 3°C / second max   |  |
| Preheat Temperature Min (Ts <sub>min</sub> )                 | 150°C              |  |
| Preheat Temperature Max (Ts <sub>max</sub> )                 | 200°C              |  |
| Preheat Time (ts <sub>min</sub> to ts <sub>max</sub> )       | 60 - 180 seconds   |  |
| Temperature (T <sub>L</sub> )                                | 217°C              |  |
| Time Maintained Above Temperature $T_L$ $(t_L)$              | 60 - 150 seconds   |  |
| Peak / Classification Temperature $(T_p)$                    | 260°C              |  |
| Time Within 5°C of Actual Peak Temperature (t <sub>p</sub> ) | 20 - 40 seconds    |  |
| Ramp - Down Rate   | 6°C / second max   |  |
| Time 25°C to Peak Temperature                                | 8 minutes max      |  |

#### Notes for Table 7:

- All temperatures refer to the application Printed Circuit Board (PCB), measured on the surface adjacent to the package body.

## Mechanical Dimensions





Figure I. Package outline drawing.

#### Notes for Figure 1:

- Do not handle the device by the lens—care must be taken to avoid damage to the lens or the interior of the device that can be damaged by excessive force to the lens.
- Drawings not to scale.
- All dimensions are in millimeters.
- The Thermal Pad is electrically isolated from the Anode and Cathode contact pads.

# Pad Configuration



| PAD | FUNCTION |
|-----|----------|
|     | CATHODE  |
| 2   | ANODE    |
| 3   | THERMAL  |

Figure 2. Pad configuration.

#### Note for Figure 2:

- The Thermal Pad is electrically isolated from the Anode and Cathode contact pads.

### Solder Pad Design




Figure 3. Solder pad layout.

#### Note for Figure 3:

- The photograph below shows the recommended LUXEON Rebel layout on Printed Circuit Board (PCB). This design easily achieves a thermal resistance of 7K/W.
- Application Brief AB32 provides extensive details for this layout. In addition, the .dwg files are available at www.philipslumileds.com and www.philipslumileds.cn.com.

# Wavelength Characteristics

## Cool-White at Test Current Thermal Pad Temperature = 25°C




Figure 4a. Cool-white color spectrum of typical CCT part, integrated measurement

## Neutral-White at Test Current Thermal Pad Temperature = 25°C




Figure 4b. Neutral-white color spectrum of typical CCT part, integrated measurement.

# Typical Light Output Characteristics over Temperature

### Cool-White and Neutral-White at Test Current




Figure 5. Relative luminous flux vs. thermal pad temperature.

# Typical Forward Current Characteristics

## Cool-White and Neutral-White Thermal Pad Temperature = 25°C




Figure 6. Forward current vs. forward voltage.

# Typical Relative Luminous Flux

# Typical Relative Luminous Flux vs. Forward Current for Cool-White and Neutral-White Thermal Pad Temperature = 25°C




Figure 7. Relative luminous flux or radiometric power vs. forward current for cool-white and neutral-white, Thermal Pad = 25°C maintained.

# Current Derating Curves

# Current Derating Curve for 350 mA Drive Current Cool-White and Neutral-White




Figure 8. Maximum forward current vs. ambient temperature, based on T<sub>IMAX</sub> = 150°C.

# Current Derating Curve for 700 mA Drive Current Cool-White and Neutral-White




Figure 9. Maximum forward current vs. ambient temperature, based on T<sub>IMAX</sub> = 150°C.

1. Current derating curves represent constant current operation condition.

# Current Derating Curve for 1000 mA Drive Current Cool-White and Neutral-White




Figure 10. Maximum forward current vs. ambient temperature, based on  $T_{\rm JMAX}$  = 150°C.

# Typical Radiation Patterns

# Typical Spatial Radiation Pattern for Cool-White and Neutral-White Lambertian




Figure IIa. Typical representative spatial radiation pattern for cool-white and neutral-white lambertian.

## Typical Polar Radiation Pattern for White Lambertain




Figure 11b. Typical polar radiation pattern for cool-white and neutral-white lambertian.

# Emitter Pocket Tape Packaging




Figure 13. Emitter pocket tape packaging

# Emitter Reel Packaging




Figure 14. Emitter reel packageing

# Product Binning and Labeling

#### **Purpose of Product Binning**

In the manufacturing of semiconductor products, there is a variation of performance around the average values given in the technical data sheets. For this reason, Philips Lumileds bins the LED components for luminous flux, color and forward voltage  $(V_r)$ .

#### **Decoding Product Bin Labeling**

LUXEON Rebel emitters are labeled using a three or four digit alphanumeric code (CAT code) depicting the bin values for emitters packaged on a single reel. All emitters packaged within a reel are of the same 3-variable bin combination. Using these codes, it is possible to determine optimum mixing and matching of products for consistency in a given application.

Reels of Cool-White and Neutral-White emitters are labeled with a four digit alphanumeric CAT code following the format below.

#### ABCD

A = Flux bin (J, K, L, M etc.) B and C = Color bin (W0, U0, V0 etc.) D =  $V_r$  bin (D, E, F, G etc.)

## Luminous Flux Bins

Table 8 lists the standard photometric luminous flux bins for LUXEON Rebel emitters (tested and binned at 350 mA).

Although several bins are outlined, product availability in a particular bin varies by production run and by product performance. Not all bins are available in all colors.

|          | Table 8.                 |                          |  |  |  |  |  |
|----------|--------------------------|--------------------------|--|--|--|--|--|
|          | Flux Bins                |                          |  |  |  |  |  |
|          | Minimum Photometric Flux | Maximum Photometric Flux |  |  |  |  |  |
| Bin Code | (lm)                     | (lm)                     |  |  |  |  |  |
| Н        | 50                       | 60                       |  |  |  |  |  |
| J        | 60                       | 70                       |  |  |  |  |  |
| K        | 70                       | 80                       |  |  |  |  |  |
| L        | 80                       | 90                       |  |  |  |  |  |
| M        | 90                       | 100                      |  |  |  |  |  |
| N        | 100                      | 110                      |  |  |  |  |  |
| X        | 110                      | 120                      |  |  |  |  |  |
| Р        | 120                      | 130                      |  |  |  |  |  |
| Y        | 130                      | 140                      |  |  |  |  |  |
| Q        | 140                      | 150                      |  |  |  |  |  |
| R        | 150                      | 160                      |  |  |  |  |  |
| S        | 180                      | 200                      |  |  |  |  |  |

### Cool-White Bin Structure




Figure 15. Cool-White bin structure.

Cool-White LUXEON Rebel emitters are tested and binned by x,y coordinates. 19 Color Bins, CCT Range 4,500K to 10,000K.

Table 9.

|          |          | Со       | ol-White Bin Co | oordinates |          |          |             |
|----------|----------|----------|-----------------|------------|----------|----------|-------------|
|          |          |          | Typical CCT     |            |          |          | Typical CCT |
| Bin Code | ×        | Υ        | (K)             | Bin Code   | X        | Υ        | (K)         |
|          | 0.274238 | 0.300667 |                 |            | 0.318606 | 0.310201 |             |
| YO       | 0.303051 | 0.332708 | 8000            | WQ         | 0.329393 | 0.320211 | 6000        |
|          | 0.307553 | 0.310778 |                 |            | 0.329544 | 0.310495 |             |
|          | 0.282968 | 0.283772 |                 |            | 0.319597 | 0.301303 |             |
|          | 0.282968 | 0.283772 |                 |            | 0.328636 | 0.368952 |             |
| YA       | 0.307553 | 0.310778 | 8000            | VM         | 0.348147 | 0.385629 | 5300        |
|          | 0.311163 | 0.293192 |                 |            | 0.346904 | 0.371742 |             |
|          | 0.289922 | 0.270316 |                 |            | 0.328823 | 0.356917 |             |
|          | 0.301093 | 0.342244 |                 |            | 0.328823 | 0.356917 |             |
| XM       | 0.313617 | 0.354992 | 6700            | VN         | 0.346904 | 0.371742 | 5300        |
|          | 0.314792 | 0.344438 |                 |            | 0.345781 | 0.359190 |             |
|          | 0.303051 | 0.332708 |                 |            | 0.329006 | 0.345092 |             |
|          | 0.303051 | 0.332708 |                 |            | 0.329006 | 0.345092 |             |
| XN       | 0.314792 | 0.344438 | 6700            | VO         | 0.345781 | 0.359190 | 5300        |
|          | 0.316042 | 0.333222 |                 |            | 0.344443 | 0.344232 |             |
|          | 0.305170 | 0.322386 |                 |            | 0.329220 | 0.331331 |             |
|          | 0.305170 | 0.322386 |                 |            | 0.329220 | 0.331331 |             |
| X0       | 0.316042 | 0.333222 | 6700            | VP         | 0.344443 | 0.344232 | 5300        |
|          | 0.317466 | 0.320438 |                 |            | 0.343352 | 0.332034 |             |
|          | 0.307553 | 0.310778 |                 |            | 0.329393 | 0.320211 |             |
|          | 0.307553 | 0.310778 |                 |            | 0.348147 | 0.385629 |             |
| XP       | 0.317466 | 0.320438 | 6700            | UM         | 0.367294 | 0.400290 | 4750        |
|          | 0.319597 | 0.301303 |                 |            | 0.364212 | 0.382878 |             |
|          | 0.311163 | 0.293192 |                 |            | 0.346904 | 0.371742 |             |
|          | 0.313617 | 0.354992 |                 |            | 0.346904 | 0.371742 |             |
| WM       | 0.328636 | 0.368952 | 6000            | UN         | 0.364212 | 0.382878 | 4750        |
|          | 0.328823 | 0.356917 |                 |            | 0.362219 | 0.371616 |             |
|          | 0.314792 | 0.344438 |                 |            | 0.345781 | 0.359190 |             |
|          | 0.314792 | 0.344438 |                 |            | 0.345781 | 0.359190 |             |
| WN       | 0.328823 | 0.356917 | 6000            | U0         | 0.362219 | 0.371616 | 4750        |
|          | 0.329006 | 0.345092 |                 |            | 0.359401 | 0.355699 |             |
|          | 0.316042 | 0.333222 |                 |            | 0.344443 | 0.344232 |             |
|          | 0.316042 | 0.333222 |                 |            | 0.344443 | 0.344232 |             |
| WO       | 0.329006 | 0.345092 | 6000            | UP         | 0.359401 | 0.355699 | 4750        |
|          | 0.329220 | 0.331331 |                 |            | 0.357079 | 0.342581 |             |
|          | 0.317466 | 0.320438 |                 |            | 0.343352 | 0.332034 |             |
|          | 0.317466 | 0.320438 |                 |            |          |          |             |
| WP       | 0.329220 | 0.331331 | 6000            |            |          |          |             |
| • • •    | 0.329393 | 0.320211 | <del>-</del>    |            |          |          |             |
|          | 0.318606 | 0.310201 |                 |            |          |          |             |

#### Note for Table 9:

- Philips Lumileds maintains a tester tolerence of  $\pm\ 0.005$  on x, y color coordinates.

### Neutral-White Bin Structure

Neutral-White LUXEON Rebel emitters are tested and binned by x,y coordinates. 12 Color Bins, CCT Range 3,500K to 4,500K.




Figure 16. Neutral-White bin structure.

Table 10.

| Neutral-White Bin Coordinates |          |          |             |          |          |          |             |  |
|-------------------------------|----------|----------|-------------|----------|----------|----------|-------------|--|
|                               |          |          | Typical CCT |          |          |          | Typical CCT |  |
| Bin Code                      | ×        | Υ        | (K)         | Bin Code | X        | Υ        | (K)         |  |
|                               | 0.367294 | 0.400290 |             |          | 0.378264 | 0.382458 |             |  |
| TM                            | 0.385953 | 0.412995 | 4300        | SO       | 0.392368 | 0.390932 | 3950        |  |
|                               | 0.381106 | 0.393747 |             |          | 0.387071 | 0.373899 |             |  |
|                               | 0.364212 | 0.382878 |             |          | 0.374075 | 0.365822 |             |  |
|                               | 0.364212 | 0.382878 |             |          | 0.374075 | 0.365822 |             |  |
| TN                            | 0.381106 | 0.393747 | 4300        | SP       | 0.387071 | 0.373899 | 3950        |  |
|                               | 0.378264 | 0.382458 |             |          | 0.382598 | 0.359515 |             |  |
|                               | 0.362219 | 0.371616 |             |          | 0.370582 | 0.351953 |             |  |
|                               | 0.362219 | 0.371616 |             |          | 0.402270 | 0.422776 |             |  |
| TO                            | 0.378264 | 0.382458 | 4300        | RM       | 0.420940 | 0.432618 | 3650        |  |
|                               | 0.374075 | 0.365822 |             |          | 0.414776 | 0.416097 |             |  |
|                               | 0.359401 | 0.355699 |             |          | 0.396279 | 0.403508 |             |  |
|                               | 0.359401 | 0.355699 |             |          | 0.396279 | 0.403508 |             |  |
| TP                            | 0.374075 | 0.365822 | 4300        | RN       | 0.414776 | 0.416097 | 3650        |  |
|                               | 0.370582 | 0.351953 |             |          | 0.408593 | 0.399525 |             |  |
|                               | 0.357079 | 0.342581 |             |          | 0.392368 | 0.390932 |             |  |
|                               | 0.385953 | 0.412995 |             |          | 0.392368 | 0.390932 |             |  |
| SM                            | 0.402270 | 0.422776 | 3950        | R0       | 0.408593 | 0.399525 | 3650        |  |
|                               | 0.396279 | 0.403508 |             |          | 0.402113 | 0.382156 |             |  |
|                               | 0.381106 | 0.393747 |             |          | 0.387071 | 0.373899 |             |  |
|                               | 0.381106 | 0.393747 |             |          | 0.387071 | 0.373899 |             |  |
| SN                            | 0.396279 | 0.403508 | 3950        | RP       | 0.402113 | 0.382156 | 3650        |  |
|                               | 0.392368 | 0.390932 |             |          | 0.396564 | 0.367284 |             |  |
|                               | 0.378264 | 0.382458 |             |          | 0.382598 | 0.359515 |             |  |

#### Note for Table 10:

- Philips Lumileds maintains a tester tolerence of  $\pm$  0.005 on x, y color coordinates.

# Forward Voltage Bins

Table 11 lists minimum and maximum  $V_f$  bin values per emitter. Although several bins are outlined, product availability in a particular bin varies by production run and by product performance.

Table 11.

| V <sub>f</sub> Bins     |  |   |  |  |  |  |
|-------------------------|--|---|--|--|--|--|
| Minimum Forward Voltage | Maximum Forward Voltage  |   |  |  |  |  |
| (V)                     | (V)  |   |  |  |  |  |
| 2.55                    | 2.79   |   |  |  |  |  |
| 2.79                    | 3.03   |   |  |  |  |  |
| 3.03                    | 3.27   |   |  |  |  |  |
| 3.27                    | 3.51   |   |  |  |  |  |
| 3.51                    | 3.75   |   |  |  |  |  |
| 3.75                    | 3.99   |   |  |  |  |  |
|                         | V <sub>f</sub> Bins  Minimum Forward Voltage (V)  2.55 2.79 3.03 3.27 3.51 | V <sub>r</sub> Bins       Minimum Forward Voltage<br>(V)     Maximum Forward Voltage<br>(V)       2.55     2.79       2.79     3.03       3.03     3.27       3.27     3.51       3.51     3.75 |  |  |  |  |

### Who We Are

Philips Lumileds focuses on one goal: Creating the world's highest performing LEDs. The company pioneered the use of solid-state lighting in breakthrough products such as the first LED backlit TV, the first LED flash in camera phones, and the first LED daytime running lights for cars. Today we offer the most comprehensive portfolio of high quality LEDs and uncompromising service.

Philips Lumileds brings LED's qualities of energy efficiency, digital control and long life to spotlights, downlights, high bay and low bay lighting, indoor area lighting, architectural and specialty lighting as well as retrofit lamps. Our products are engineered for optimal light quality and unprecedented efficacy at the lowest overall cost. By offering LEDs in chip, packaged and module form, we deliver supply chain flexibility to the inventors of next generation illumination.

Philips Lumileds understands that solid state lighting is not just about energy efficiency. It is about elegant design. Reinventing form. Engineering new materials. Pioneering markets and simplifying the supply chain. It's about a shared vision. Learn more about our comprehensive portfolio of LEDs at www.philipslumileds.com.

©2014 Philips Lumileds Lighting Company. All rights reserved. Product specifications are subject to change without notice. LUXEON is a registered trademark of the Philips Lumileds Lighting Company in the United States and other countries.

