





METRINCH®

IF THIS CAN'T DO IT, NO TOOL CAN



The Difference that counts

A nut or a bolt has flats and corners. The corners are more easily damaged and do not offer the optimum grip for a tool. In developing the Metrinch tool system Jozef Ruzicka had the aim to design sockets and spanners, which would not only have longer effective life, but would also ensure minimal damage to the fasteners on which they are used.



The patented Metrinch Wall Drive profile drives only on the flats and not on the corners. The dimensions of Metrinch sockets and spanners have been precisely calculated, so that a single Metrinch tool will

operate on both metric and inch series fasteners. For example, with a spanner 19 mm it is possible not only to tighten or undo a metric nut or bolt, but also the inch bolts 3/4" AF, 3/8" BSW and 7/16" BSF. Even when such bolts have become worn, damaged or completely rounded by abrasion.

A further major advantage in terms of application is that the Metrinch Wall Drive profile can be used on open-end spanners as well as on sockets and ring-spanners. Metrinch open-end spanners always provide a 4-point grip instead of the 2-point grip characterizing the traditional profile.

Torque Loading



The Metrinch Wall Drive Profile was designed to provide a greater area of force application, compared with that applied by conventional tools. This profile, because of the buttress effect of its load bearing lugs, does not transmit the extreme peaks found when a tool with a wedge shaped profile is used. In distributing the torque load to the fastener through the flats, the Metrinch tool does not only achieve greater force, but also lowers the

possibility of distortion to the nut or bolt head.

Having a thin wall is an advantage in every socket. We can afford to provide such a wall, because with Metrinch spanners and sockets the force is absorbed where the wall has its greatest strength. Metrinch sockets are capable of exceeding the tightening torques specified in the DIN standard by 70 to 100 %, depending on the socket size.

Quality & Safety

The Metrinch Wall Drive profile is not the only feature we rely on. The steel our tools are made of forms another important aspect. To achieve the best, it is imperative to use a steel alloy this being chrome vanadium 46CrV4, which provides a margin of safety, particularly in conditions involving extreme stresses.

We also attach great value to product finish, all our tools are chrome-plated and polished. This is not just for visual reasons, but because it provides the most effective protection against rust, even in extreme conditions. We take the principles of on-the-job safety and accident prevention very seriously.



The patented Metrinch Wall Drive profile has been precisely calculated to ensure a secure and even application of torque to the flats of a nut or bolt and not to the corners.

In most instances the greater the force applied to a Metrinch tool the more positive the grip becomes thus minimising the risk of injury to an operator which may be caused through a socket or a spanner slipping off a fastener. Laboratory test results prove that torque loadings of 1.5 times greater than those possible with a conventional socket can be achieved using a Metrinch tool.

Quality Assurance and Guarantee

All Metrinch tools are forged from high quality Chrome Vanadium Alloy Steel, and meet with the torque and hardness requirements necessary with the relevant international standards, DIN, U.S. Federal Specification and British Standard. Our factory has an exacting quality assurance program, monitored by a highly trained technical staff using the most up to date laboratory equipment. Constant inspections are made during the stages in the

production process, and we make a 100% check of all components at the time of packing to make sure that our high standards are maintained. Metrinch tools are used all over the world, and carry an unconditional worldwide free replacement guarantee if for any reason a tool happens to fail.



Award Winner

Discerning judges in Germany granted the Metrinch tool system the coveted award for innovation in design at Munich in 1991. We regard it a great honour to be recognised in a country which is renowned for producing some of the finest hand tools in the world.



Applications of Metrinch sockets & combination spanners:

| METRIC (MM) | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 | 26 | 27 | 28 | 29 | 30 | 31 | 32 | |
|---------------|------|------|-----|------|------|-------|-----|------|-------|-----|------|-------|------|-------|-------|-----|-------|-------|-----|-------|-------|------|--------|--------|-------|--------|--------|--------|-------|--|
| INCH (SAE AF) | 5/32 | 3/16 | 1/4 | 9/32 | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 25/32 | 13/16 | 7/8 | 29/32 | 15/16 | 1 | 1 1/16 | 1 1/32 | 1 1/8 | 1 5/32 | 1 3/16 | 1 1/32 | 1 1/4 | |
| BSW | | | | | | 1/8 | | 3/16 | | | 1/4 | | 5/16 | | | 3/8 | 7/16 | | 1/2 | | | 9/16 | | 5/8 | | | 1/16 | | | |
| BS BSF | | | | | | | | | 1/4 | | | 5/16 | | 5/8 | | | 7/16 | | 1/2 | | 9/16 | | | 5/8 | | | 1 1/16 | | 5/4 | |
| BA | | | 6BA | 4BA | 3BA | 2BA | | 0BA | | | | | | | | | | | | | | | | | | | | | | |

Cendai

The company Cendai was founded in 1972 and has specialized in the production of sockets and accessories. Cendai produces annually more than 6 million sockets, 8 million accessories and 800.000 other tool sets. In total every month over 20 million parts are produced.

The Cendai facility has a total area of 36.000 m² of which 20.000 m² is in use for production and assembly. At any given time the facility can accommodate fifty 40ft containers at the same time. Cendai is not only the largest manufacturer of sockets in Asia, but also the most modern factory with the latest sophisticated machinery.

All the hand tools are made to the highest international standards whereby a strict quality control is applied.

Cendai is ISO 9002 Certified.

CONTENTS

| PRODUCT | PAGE |
|----------------------------|---------|
| Combination spanners | 4 |
| 1/4" Sockets & accessories | 4 |
| 3/8" Sockets & accessories | 5 |
| 1/2" Sockets & accessories | 6 |
| VDE Sockets & accessories | 7 |
| Impact sockets | 7 |
| Cliprail sets | 8 - 9 |
| Spanner sets | 10 |
| Socket & combinationsets | 11 - 14 |
| VDE sets | 14 |
| Impact sets | 15 |



Combination spanners



| Part no. | MM | INCH |
|----------|----|-------|
| MET-1108 | 8 | 5/16 |
| MET-1109 | 9 | 11/32 |
| MET-1110 | 10 | 3/8 |
| MET-1111 | 11 | 7/16 |
| MET-1112 | 12 | 15/32 |
| MET-1113 | 13 | 1/2 |

| Part no. | MM | INCH |
|----------|----|-------|
| MET-1114 | 14 | 9/16 |
| MET-1115 | 15 | 19/32 |
| MET-1116 | 16 | 5/8 |
| MET-1117 | 17 | 11/16 |

| Part no. | MM | INCH |
|----------|---------|-------|
| MET-1118 | 18 | 23/32 |
| MET-1119 | 19 | 3/4 |
| MET-1120 | 20 / 21 | 13/16 |
| MET-1122 | 22 / 23 | 7/8 |

| Part no. | MM | INCH |
|----------|---------|-------|
| MET-1124 | 24 | 15/16 |
| MET-1126 | 26 / 27 | 13/16 |
| MET-1129 | 29 / 30 | 13/16 |
| MET-1132 | 31 / 32 | 13/16 |



1/4" Sockets

| Part no. | MM | INCH |
|----------|----|-------|
| MET-1404 | 4 | 5/32 |
| MET-1405 | 5 | 3/16 |
| MET-1406 | 6 | 1/4 |
| MET-1407 | 7 | 9/32 |
| MET-1408 | 8 | 5/16 |
| MET-1409 | 9 | 11/32 |
| MET-1410 | 10 | 3/8 |
| MET-1411 | 11 | 7/16 |
| MET-1412 | 12 | 15/32 |
| MET-1413 | 13 | 1/2 |

1/4" Sockets deep

| Part no. | MM | INCH |
|----------|----|-------|
| MET-1454 | 4 | 5/32 |
| MET-1455 | 5 | 3/16 |
| MET-1456 | 6 | 1/4 |
| MET-1457 | 7 | 9/32 |
| MET-1458 | 8 | 5/16 |
| MET-1459 | 9 | 11/32 |
| MET-1460 | 10 | 3/8 |
| MET-1461 | 11 | 7/16 |
| MET-1462 | 12 | 15/32 |
| MET-1463 | 13 | 1/2 |

1/4" Accessories

| Part no. | DESCRIPTION |
|------------|---------------------------------|
| MET-1488 | EXTENSION 75 MM |
| MET-1490 | RATCHET |
| MET-1490SN | REPAIR SET FOR Q.R. RATCHET |
| MET-1491 | FINGERTIGHT RATCHET |
| MET-1492 | JOINT |
| MET-1493 | EXTENSION 50 MM |
| MET-1494 | 1/4" MALE & 3/8" FEMALE ADAPTER |
| MET-1495 | SPINNER HANDLE |
| MET-1496 | EXTENSION 150 MM |
| MET-1497 | T-PIECE |
| MET-1498 | BIT HOLDER |
| MET-1499 | EXTENSION 100 MM WOBBLE |





3/8" Sockets

| Part no. | MM | INCH |
|----------|---------|-------|
| MET-1308 | 8 | 5/16 |
| MET-1309 | 9 | 11/32 |
| MET-1310 | 10 | 3/8 |
| MET-1311 | 11 | 7/16 |
| MET-1312 | 12 | 15/32 |
| MET-1313 | 13 | 1/2 |
| MET-1314 | 14 | 9/16 |
| MET-1315 | 15 | 19/32 |
| MET-1316 | 16 | 5/8 |
| MET-1317 | 17 | 11/16 |
| MET-1318 | 18 | 23/32 |
| MET-1319 | 19 | 3/4 |
| MET-1320 | 20 / 21 | 13/16 |
| MET-1322 | 22 | 7/8 |



3/8" Sockets deep

| Part no. | MM | INCH |
|----------|---------|-------|
| MET-1350 | 10 | 3/8 |
| MET-1351 | 11 | 7/16 |
| MET-1352 | 12 | 15/32 |
| MET-1353 | 13 | 1/2 |
| MET-1354 | 14 | 9/16 |
| MET-1355 | 15 | 19/32 |
| MET-1356 | 16 | 5/8 |
| MET-1357 | 17 | 11/16 |
| MET-1358 | 18 | 23/32 |
| MET-1359 | 19 | 3/4 |
| MET-1360 | 20 / 21 | 13/16 |
| MET-1362 | 22 | 7/8 |



3/8" Accessories

| Part no. | DESCRIPTION |
|------------|---------------------------------|
| MET-1387 | EXTENSION 125 MM |
| MET-1388 | EXTENSION 75 MM WOBBLE |
| MET-1390 | RATCHET |
| MET-1390SN | REPAIR SET FOR Q.R. RATCHET |
| MET-1391 | EXTENSION 75 MM |
| MET-1392 | EXTENSION 150 MM WOBBLE |
| MET-1393 | EXTENSION 150 MM |
| MET-1394 | JOINT |
| MET-1395 | SPARKPLUG SOCKET 16 MM & 5/8" |
| MET-1396 | SPARKPLUG SOCKET 21 MM & 13/16" |
| MET-1397 | EXTENSION 250 MM WOBBLE |
| MET-1398 | T-PIECE |
| MET-1399 | EXTENSION 40 MM WOBBLE |

**1/2" Sockets**

| Part no. | MM | INCH |
|-----------------|---------|--------|
| MET-1210 | 10 | 3/8 |
| MET-1211 | 11 | 7/16 |
| MET-1212 | 12 | 15/32 |
| MET-1213 | 13 | 1/2 |
| MET-1214 | 14 | 9/16 |
| MET-1215 | 15 | 19/32 |
| MET-1216 | 16 | 5/8 |
| MET-1217 | 17 | 11/16 |
| MET-1218 | 18 | 23/32 |
| MET-1219 | 19 | 3/4 |
| MET-1220 | 20 / 21 | 13/16 |
| MET-1222 | 22 | 7/8 |
| MET-1223 | 23 | 29/32 |
| MET-1224 | 24 | 15/16 |
| MET-1225 | 25 | 1 |
| MET-1226 | 26 / 27 | 13/16 |
| MET-1228 | 28 | 1 1/8 |
| MET-1229 | 29 / 30 | 1 3/16 |
| MET-1231 | 31 / 32 | 1 1/4 |

**1/2" Sockets deep**

| Part no. | MM | INCH |
|-----------------|---------|--------|
| MET-1250 | 10 | 3/8 |
| MET-1251 | 11 | 7/16 |
| MET-1252 | 12 | 15/32 |
| MET-1253 | 13 | 1/2 |
| MET-1254 | 14 | 9/16 |
| MET-1255 | 15 | 19/32 |
| MET-1256 | 16 | 5/8 |
| MET-1257 | 17 | 11/16 |
| MET-1258 | 18 | 23/32 |
| MET-1259 | 19 | 3/4 |
| MET-1260 | 20 / 21 | 13/16 |
| MET-1262 | 22 | 7/8 |
| MET-1263 | 23 | 29/32 |
| MET-1264 | 24 | 15/16 |
| MET-1265 | 25 | 1 |
| MET-1267 | 26 / 27 | 13/16 |
| MET-1268 | 28 | 1 1/8 |
| MET-1270 | 29 / 30 | 1 3/16 |
| MET-1272 | 31 / 32 | 1 1/4 |

1/2" Accessories

| Part no. | DESCRIPTION |
|-------------------|---------------------------------|
| MET-1287 | EXTENSION 75 MM |
| MET-1288 | EXTENSION 75 MM WOBBLE |
| MET-1290 | RATCHET |
| MET-1290SN | REPAIR SET FOR Q.R.RATCHET |
| MET-1291 | EXTENSION 250 MM |
| MET-1292 | SPARKPLUG SOCKET 16 MM & 5/8" |
| MET-1293 | SPARKPLUG SOCKET 21 MM & 13/16" |
| MET-1294 | T-PIECE |
| MET-1295 | BREAKER BAR 410 MM |
| MET-1296 | JOINT |
| MET-1297 | EXTENSION 125 MM |
| MET-1298 | 1/2" FEMALE & 3/8" MALE ADAPTER |
| MET-1299 | EXTENSION 125 MM WOBBLE |





1/2" Sockets VDE

| Part no. | MM | INCH |
|-----------|---------|-------|
| MET-1210E | 10 | 3/8" |
| MET-1213E | 13 | 1/2 |
| MET-1214E | 14 | 9/16 |
| MET-1216E | 16 | 5/8 |
| MET-1217E | 17 | 11/16 |
| MET-1219E | 19 | 3/4 |
| MET-1220E | 20 / 21 | 13/16 |

1/2" Accessories VDE

| Part no. | DESCRIPTION |
|-----------|----------------------|
| MET-1290E | RATCHET VDE |
| MET-1297E | EXTENSION 125 MM VDE |



Impact sockets

1/2"

| Part no. | MM | INCH |
|----------|----|-------|
| MET-2210 | 10 | 3/8 |
| MET-2211 | 11 | 7/16 |
| MET-2212 | 12 | 15/32 |
| MET-2213 | 13 | 1/2 |
| MET-2214 | 14 | 9/16 |
| MET-2215 | 15 | 19/32 |
| MET-2216 | 16 | 5/8 |
| MET-2217 | 17 | 11/16 |
| MET-2218 | 18 | 23/32 |
| MET-2219 | 19 | 3/4 |
| MET-2220 | 20 | 25/32 |
| MET-2221 | 21 | 13/16 |
| MET-2222 | 22 | 7/8 |
| MET-2223 | 23 | 29/32 |
| MET-2224 | 24 | 15/16 |
| MET-2225 | 25 | 1 |
| MET-2227 | 27 | 11/16 |
| MET-2228 | 28 | 11/8 |
| MET-2230 | 30 | 13/16 |
| MET-2232 | 32 | 11/4 |

3/8"

| Part no. | MM | INCH |
|----------|----|-------|
| MET-2310 | 10 | 3/8 |
| MET-2311 | 11 | 7/16 |
| MET-2312 | 12 | 15/32 |
| MET-2313 | 13 | 1/2 |
| MET-2314 | 14 | 9/16 |
| MET-2315 | 15 | 19/32 |
| MET-2316 | 16 | 5/8 |
| MET-2317 | 17 | 11/16 |
| MET-2318 | 18 | 23/32 |
| MET-2319 | 19 | 3/4 |
| MET-2320 | 20 | 25/32 |
| MET-2321 | 21 | 13/16 |
| MET-2322 | 22 | 7/8 |



Impact sockets deep

1/2"

| Part no. | MM | INCH |
|----------|----|-------|
| MET-2250 | 10 | 3/8 |
| MET-2251 | 11 | 7/16 |
| MET-2252 | 12 | 15/32 |
| MET-2253 | 13 | 1/2 |
| MET-2254 | 14 | 9/16 |
| MET-2255 | 15 | 19/32 |
| MET-2256 | 16 | 5/8 |
| MET-2257 | 17 | 11/16 |
| MET-2258 | 18 | 23/32 |
| MET-2259 | 19 | 3/4 |
| MET-2260 | 20 | 25/32 |
| MET-2261 | 21 | 13/16 |
| MET-2262 | 22 | 7/8 |
| MET-2263 | 23 | 29/32 |
| MET-2264 | 24 | 15/16 |
| MET-2265 | 25 | 1 |
| MET-2267 | 27 | 11/16 |
| MET-2268 | 28 | 11/8 |
| MET-2270 | 30 | 13/16 |
| MET-2272 | 32 | 11/4 |

3/8"

| Part no. | MM | INCH |
|----------|----|-------|
| MET-2350 | 10 | 3/8 |
| MET-2351 | 11 | 7/16 |
| MET-2352 | 12 | 15/32 |
| MET-2353 | 13 | 1/2 |
| MET-2354 | 14 | 9/16 |
| MET-2355 | 15 | 19/32 |
| MET-2356 | 16 | 5/8 |
| MET-2357 | 17 | 11/16 |
| MET-2358 | 18 | 23/32 |
| MET-2359 | 19 | 3/4 |
| MET-2360 | 20 | 25/32 |
| MET-2361 | 21 | 13/16 |
| MET-2362 | 22 | 7/8 |



MET-0220 Cliprail set 1/4" 9 pieces

Sockets

| Content Size | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 |
|---------------|------|-----|------|------|-------|-----|------|-------|-----|
| METRIC (MM) | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 |
| INCH (SAE AF) | 3/16 | 1/4 | 5/32 | 7/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 |

| | | | | | | | | | |
|-------------|---|---|---|---|---|---|---|---|---|
| 1/4" SOCKET | • | • | • | • | • | • | • | • | • |
|-------------|---|---|---|---|---|---|---|---|---|



MET-0230 Cliprail set 1/4" 9 pieces deep

Sockets

| Content Size | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 |
|---------------|------|-----|------|------|-------|-----|------|-------|-----|
| METRIC (MM) | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 |
| INCH (SAE AF) | 3/16 | 1/4 | 5/32 | 7/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 |

| | | | | | | | | | |
|------------------|---|---|---|---|---|---|---|---|---|
| 1/4" SOCKET DEEP | • | • | • | • | • | • | • | • | • |
|------------------|---|---|---|---|---|---|---|---|---|



MET-0320 Cliprail set 3/8" 12 pieces

Sockets

| Content Size | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 |
|---------------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-------|-----|----|
| METRIC (MM) | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 |
| INCH (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 7/8 | |

| | | | | | | | | | | | | | |
|-------------|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 3/8" SOCKET | • | • | • | • | • | • | • | • | • | • | • | • | • |
|-------------|---|---|---|---|---|---|---|---|---|---|---|---|---|



MET-0321 Cliprail set 3/8" 8 pieces

Sockets

| Content Size | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
|---------------|-----|------|-------|-----|------|-------|-----|-------|
| METRIC (MM) | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
| INCH (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 |

| | | | | | | | | |
|-------------|---|---|---|---|---|---|---|---|
| 3/8" SOCKET | • | • | • | • | • | • | • | • |
|-------------|---|---|---|---|---|---|---|---|



MET-0330 Cliprail set 3/8" 12 pieces deep

Sockets

| Content Size | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 |
|---------------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-------|-----|----|
| METRIC (MM) | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 |
| INCH (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 7/8 | |

| | | | | | | | | | | | | | |
|------------------|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 3/8" SOCKET DEEP | • | • | • | • | • | • | • | • | • | • | • | • | • |
|------------------|---|---|---|---|---|---|---|---|---|---|---|---|---|

**MET-0331 Cliprail set 3/8" 8 pieces deep****Sockets**

| Content | Size | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
|---------------|------|-----|------|-------|-----|------|-----|-------|-----|
| METRIC (MM) | | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
| INCH (SAE AF) | | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 |

3/8" SOCKET DEEP

• • • • • • • •

**MET-0430 Cliprail set 1/2" 10 pieces****Sockets**

| Content | Size | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 | 22 | 24 |
|---------------|------|-----|------|-------|-----|------|-----|-------|-----|-----|-------|
| METRIC (MM) | | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 | | |
| INCH (SAE AF) | | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 | 7/8 | 15/16 |

1/2" SOCKET

• • • • • • • •

**MET-0431 Cliprail set 1/2" 8 pieces****Sockets**

| Content | Size | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
|---------------|------|-----|------|-------|-----|------|-----|-------|-----|
| METRIC (MM) | | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
| INCH (SAE AF) | | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 |

1/2" SOCKET

• • • • • • • •

**MET-0440 Cliprail set 1/2" 10 pieces deep****Sockets**

| Content | Size | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 | 22 | 24 |
|---------------|------|-----|------|-------|-----|------|-----|-------|-----|-----|-------|
| METRIC (MM) | | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 | | |
| INCH (SAE AF) | | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 | 7/8 | 15/16 |

1/2" SOCKET DEEP

• • • • • • • •

**MET-0441 Cliprail set 1/2" 8 pieces deep****Sockets**

| Content | Size | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
|---------------|------|-----|------|-------|-----|------|-----|-------|-----|
| METRIC (MM) | | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
| INCH (SAE AF) | | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 |

1/2" SOCKET DEEP

• • • • • • • •



MET-0106 Combination spanner set 6 pieces

Combination spanners

| Content | Size | METRIC (MM) | 10 | 11 | 13 | 14 | 16 | 17 |
|---------|------|---------------------|-----|------|-----|------|-----|-------|
| Content | Size | INCH (SAE AF) | 5/8 | 7/16 | 1/2 | 9/16 | 5/8 | 11/16 |
| Content | Size | COMBINATION SPANNER | • | • | • | • | • | • |



MET-0107 Combination spanner set 7 pieces

Combination spanners

| Content | Size | METRIC (MM) | 10 | 11 | 13 | 14 | 16 | 17 | 19 |
|---------|------|---------------------|-----|------|-----|------|-----|-------|-----|
| Content | Size | INCH (SAE AF) | 5/8 | 7/16 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 |
| Content | Size | COMBINATION SPANNER | • | • | • | • | • | • | • |



MET-0110 Combination spanner set 10 pieces

Combination spanners

| Content | Size | METRIC (MM) | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 |
|---------|------|---------------------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|
| Content | Size | INCH (SAE AF) | 5/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 |
| Content | Size | COMBINATION SPANNER | • | • | • | • | • | • | • | • | • | • |



MET-0125 Combination spanner set 14 pieces

Combination spanners

| Content | Size | METRIC (MM) | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 |
|---------|------|---------------------|------|-------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-------|-------|-----|----|
| Content | Size | INCH (SAE AF) | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 15/16 | 7/8 | |
| Content | Size | COMBINATION SPANNER | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • |



MET-0135 Combination spanner set 15 pieces

Combination spanners

| Content | Size | METRIC (MM) | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 | 26 | 27 | 28 | 29 | 30 | 31 | 32 |
|---------|------|---------------------|------|-------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-----|-------|--------|--------|--------|---------|-------|----|----|----|----|----|----|
| Content | Size | INCH (SAE AF) | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 7/8 | 15/16 | 1 1/16 | 1 3/16 | 1 7/16 | 1 15/16 | 1 1/4 | | | | | | |
| Content | Size | COMBINATION SPANNER | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | |



MET-0076 Combination set

1/2" & 3/8" & 1/4" 76 pieces

Accessories

| | | |
|--------------------------|--|--|
| 1/2" | 3/8" | 1/4" |
| MET-1290 RATCHET | MET-1390 RATCHET | MET-1491 FINGERTIGHT RATCHET |
| MET-1291 EXTENSION 250MM | MET-1391 EXTENSION 75MM | MET-1492 UNIVERSAL JOINT |
| MET-1294 T-PIECE | MET-1394 UNIVERSAL JOINT | MET-1493 EXTENSION 50MM |
| | MET-1395 SPARKPLUG SOCKET 16 MM & 5/8" | MET-1494 1/4" MALE & 3/8" FEMALE ADAPTOR |
| | MET-1396 SPARKPLUG SOCKET 21 MM & 13/16" | MET-1495 SPINNER HANDLE |

Sockets & combination spanners

| Content Size | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 24 | 25 | 26 | 27 | 29 | 30 | 31 | 32 |
|---------------------|------|-----|------|------|-------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-------|-----|-------|----|--------|-------|-------|--------|-------|-------|-------|
| METRIC (MM) | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 24 | 25 | 26 | 27 | 29 | 30 | 31 | 32 |
| INCH (SAE AF) | 3/16 | 1/4 | 9/32 | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 7/8 | 15/16 | 1 | 1 1/16 | 1 1/8 | 1 1/4 | 1 1/16 | 1 1/8 | 1 1/4 | 1 1/8 |
| 1/4" SOCKET | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * |
| 1/4" SOCKET DEEP | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * |
| 3/8" SOCKET | | | | | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | | | | |
| 3/8" SOCKET DEEP | | | | | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | | | | |
| 1/2" SOCKET | | | | | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * |
| COMBINATION SPANNER | | | | | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | | | | |

MET-0248 Socket set 1/4" 48 pieces

Sockets

| Content Size | METRIC (MM) | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 |
|------------------|-------------|------|-----|------|------|-------|-----|------|-------|-----|------|
| INCH (SAE AF) | 5/32 | 3/16 | 1/4 | 9/32 | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 |
| 1/4" SOCKET | * | * | * | * | * | * | * | * | * | * | * |
| 1/4" SOCKET DEEP | * | * | * | * | * | * | * | * | * | * | * |

Accessories

| 1/4" | BITS: SIZES | | | | | |
|----------------------------------|-------------|-----|-----|-----|-----|-------------|
| MET-1486 SPINNER HANDLE MAGNETIC | FL | 4,0 | 4,5 | 5,5 | 6,5 | MM |
| MET-1490 RATCHET | PZ | 0 | I | 2 | 3 | |
| MET-1493 EXTENSION 50 MM | PH | 0 | I | 2 | 3 | |
| MET-1496 EXTENSION 150 MM | HX | 2,5 | 3,0 | 4,0 | 5,0 | 6,0 MM |
| | TX | 10 | 15 | 20 | 25 | 27 30 |
| | | | | | | BIT ADAPTOR |

MET-0300 Socket set 3/8" & 1/4" 25 pieces

Sockets

| Content Size | METRIC (MM) | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 | 20 | 21 | 22 |
|---------------|-------------|-----|------|------|-------|-----|------|-------|-----|------|-----|-------|-----|-------|-----|----|----|
| INCH (SAE AF) | 3/16 | 1/4 | 9/32 | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 | 13/16 | 7/8 | | |
| 1/4" SOCKET | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | * | |
| 3/8" SOCKET | | | | | | | | | | * | * | * | * | * | * | * | |

Accessories

| 3/8" | 1/4" | | | | | |
|--|--|--|--|--|--|--|
| MET-1390 RATCHET | MET-1491 FINGERTIGHT RATCHET | | | | | |
| MET-1392 EXTENTION 150 MM WOBBLE | MET-1492 JOINT | | | | | |
| MET-1394 UNIVERSAL JOINT | MET-1493 EXTENSION 50 MM | | | | | |
| MET-1395 SPARKPLUG SOCKET 16 MM & 5/8" | MET-1494 1/4" MALE & 3/8" FEMALE ADAPTOR | | | | | |
| MET-1396 SPARKPLUG SOCKET 21 MM & 13/16" | MET-1495 SPINNER HANDLE | | | | | |





MET-0325 Socket set 1/4" 37 pieces

Sockets

| Content Size | METRIC (MM) | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |
|---------------|-------------|-----|------|------|-------|-----|------|-------|----|
| INCH (SAE AF) | 3/16 | 1/4 | 5/32 | 7/16 | 11/32 | 3/8 | 7/16 | 15/32 | |
| 1/4" SOCKET | • | • | • | • | • | • | • | • | • |

Accessories

1/4"

- MET-1490 RATCHET
- MET-1492 JOINT
- MET-1493 EXTENSION 50 MM
- MET-1494 1/4" MALE & 3/8" FEMALE ADAPTOR
- MET-1495 SPINNER HANDLE
- MET-1497 T-PIECE
- MET-1498 HOLDER FOR BITS
- MET-1499 EXTENSION 100 MM WOBBLE

BITS: SIZES

| | | | | |
|------|-----|-----|-----|------------|
| ⊕ PH | O | I | 2 | 3 |
| ⊖ FL | 4,0 | 4,5 | 5,5 | 6,5 MM |
| ⊖ HX | 2,5 | 3,0 | 4,0 | 5,0 6,0 MM |
| ⊕ PZ | I | 2 | | |
| ⊖ TX | 10 | 15 | 20 | 25 27 30 |



MET-0427 Socket set 1/2" 26 pieces

Accessories

1/2"

- MET-1290 RATCHET
- MET-1291 EXTENSION 250MM
- MET-1292 SPARKPLUG SOCKET 16 MM & 5/8"
- MET-1293 SPARKPLUG SOCKET 21 MM & 13/16"
- MET-1294 T-PIECE
- MET-1296 JOINT
- MET-1299 EXTENSION 125 MM WOBBLE

Sockets

| Content Size | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 | 26 | 27 | 28 | 29 | 30 | 31 | 32 |
|---------------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-------|-----|-------|-------|----|--------|-------|--------|-------|----|----|----|----|
| INCH (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 7/8 | 29/32 | 15/16 | 1 | 1 1/16 | 1 1/8 | 1 3/16 | 1 1/4 | | | | |
| 1/2" SOCKET | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • |



MET-0450 Combination set 1/2" 30 pieces

Accessories

1/2"

- MET-1290 RATCHET
- MET-1293 SPARKPLUG SOCKET 21 MM & 13/16"
- MET-1295 BREAKER BAR 410 MM
- MET-1296 JOINT
- MET-1299 EXTENSION 125 MM WOBBLE

Sockets & combination spanners

| Content Size | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 | 26 | 27 | 28 | 29 | 30 | 31 | 32 |
|---------------------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-------|-----|-------|-------|----|--------|-------|--------|-------|----|----|----|----|
| INCH (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 7/8 | 29/32 | 15/16 | 1 | 1 1/16 | 1 1/8 | 1 3/16 | 1 1/4 | | | | |
| 1/2" SOCKETS | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • |
| COMBINATION SPANNER | • | • | • | • | • | • | | • | • | • | | • | | • | | • | • | • | • | • | • | • | • |



MET-0525 Socket set 3/8" 14 pieces

Sockets

| Content | Size | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
|---------------|------|------|-------|-----|------|-----|-------|-----|----|
| Metric (mm) | | | | | | | | | |
| Inch (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 | |
| 3/8" SOCKET | | • | • | • | • | • | • | • | • |

Accessories

3/8"

MET-1390 RATCHET

MET-1391 EXTENSION 75 MM

MET-1393 EXTENSION 150 MM

MET-1395 SPARKPLUG SOCKET 16 MM & 5/8"

MET-1396 SPARKPLUG SOCKET 21 MM & 13/16"

MET-1399 EXTENSION 40 MM WOBBLE



MET-0559 Combination set 1/4" & 3/8" 59 pieces

Sockets & combination spanners

| Content | Size | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 |
|---------------------|------|-----|------|------|-------|-----|------|-------|-----|------|-------|-----|-------|-------|-----|-------|-----|----|----|
| Metric (mm) | | | | | | | | | | | | | | | | | | | |
| Inch (SAE AF) | 3/16 | 1/4 | 9/32 | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | 7/8 | | |
| 1/4" SOCKET | | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • | |
| 3/8" SOCKET | | | | | | | | | | | | | | | | | | | |
| 3/8" SOCKET DEEP | | | | | | | | | | | | | | | | | | | |
| COMBINATION SPANNER | | | | | | | | | | | | | | | | | | | |

Accessories

3/8"

MET-1388 EXTENSION 75 MM WOBBLE

BIT SOCKETS: SIZES

FL 4,0 5,5 6,5 MM

PH I 2 3

PZ I 2 3

TX IO 15 20 27 30

MET-1390 RATCHET

MET-1393 EXTENSION 150 MM

MET-1394 JOINT

MET-1396 SPARKPLUG SOCKET 21 MM & 13/16"

1/4"

MET-1488 1/4" EXTENSION 75 MM

MET-1491 FINGERTIGHT RATCHET

MET-1494 1/4" MALE & 3/8" FEMALE ADAPTOR

MET-1495 SPINNER HANDLE



MET-0625 Combination set 1/4" & 3/8" 37 pieces

Sockets & combination spanners

| Content | Size | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 |
|---------------------|------|-----|------|------|-------|-----|------|-------|-----|------|-------|-----|-------|-----|
| Metric (mm) | | | | | | | | | | | | | | |
| Inch (SAE AF) | 3/16 | 1/4 | 9/32 | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 3/4 |
| 1/4" SOCKET | | • | • | • | • | • | • | • | • | • | • | • | • | • |
| 3/8" SOCKET | | | | | | | | | | | | | | |
| 3/8" SOCKET DEEP | | | | | | | | | | | | | | |
| COMBINATION SPANNER | | | | | | | | | | | | | | |

Accessories

3/8"

MET-1390 RATCHET

1/4"

MET-1494 1/4" MALE & 3/8" FEMALE ADAPTOR

MET-1495 1/4" SPINNER HANDLE

MET-1391 EXTENSION 75 MM

MET-1393 EXTENSION 150 MM

MET-1394 JOINT

MET-1395 SPARKPLUG SOCKET 16 MM & 5/8"

MET-1396 SPARKPLUG SOCKET 21 MM & 13/16"

MET-1399 EXTENSION 40 MM WOBBLE



MET-0650 Combination set 1/2" & 3/8" & 1/4" 50 pieces

Accessories

1/2"

MET-1288 EXTENSION 75 MM WOBBLE
 MET-1290 RATCHET
 MET-1291 EXTENSION 250 MM
 MET-1294 T-PIECE
 MET-1295 BREAKER BAR 410 MM
 MET-1297 EXTENSION 125 MM

3/8"

MET-1387 EXTENSION 125 MM
 MET-1390 RATCHET
 MET-1391 EXTENSION 75 MM
 MET-1394 JOINT
 MET-1395 SPARKPLUG SOCKET 16 MM & 5/8"
 MET-1396 SPARKPLUG SOCKET 21 MM & 19/16"
 MET-1399 EXTENSION 40 MM WOBBLE

1/4"

MET-1494 1/4" MALE & 3/8" FEMALE ADAPTOR
 MET-1495 1/4" SPINNER HANDLE

Sockets & combination spanners

| Content | Size | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 16 | 17 | 19 | 20 | 21 | 22 | 24 | 26 | 27 | 29 | 30 | 31 | 32 |
|---------------------|------|------|-----|------|------|-------|-----|------|-------|-----|------|-----|-------|-----|-------|-----|-------|--------|--------|-------|--------|-------|-------|----|
| Content | Size | 5/16 | 1/4 | 9/32 | 5/16 | 11/32 | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 | 13/16 | 7/8 | 15/16 | 1 1/16 | 1 3/16 | 1 1/4 | 1 3/16 | 1 1/4 | 1 1/4 | |
| Content | Size | • | • | • | • | • | • | | | | | | | | | | | | | | | | | |
| Content | Size | | | | | | | • | • | • | • | • | • | • | • | • | | | | | | | | |
| Content | Size | | | | | | | • | • | • | • | • | • | • | • | • | | | | | | | | |
| Content | Size | | | | | | | | | | | | | | | | • | • | • | • | • | • | • | • |
| Content | Size | | | | | | | | | | | | | | | | | | | | | | | |
| Content | Size | | | | | | | | | | | | | | | | | | | | | | | |
| COMBINATION SPANNER | | | | | | | • | • | • | • | • | • | • | • | | | | | | | | | | |



MET-0109E Socket set 1/2" 9 pieces VDE

Sockets

| Content | Size | METRIC (MM) | 10 | 13 | 14 | 16 | 17 | 19 | 20 | 21 |
|-----------------|------|---------------|-----|-----|------|-----|-------|-----|-------|-------|
| Content | Size | INCH (SAE AF) | 5/8 | 1/2 | 9/16 | 5/8 | 11/16 | 3/4 | 25/32 | 13/16 |
| 1/2" VDE SOCKET | | | • | • | • | • | • | • | • | • |

Accessories

1/2" VDE
 MET-1290E RATCHET VDE
 MET-1297E EXTENSION 125 MM VDE



MET-2300 Impact set 3/8" 11 pieces

Sockets

| Content | Size | METRIC (MM) | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 21 |
|---------|---------------|--------------------|------|-------|-----|------|-------|-----|-------|-------|-----|-------|----|
| | INCH (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | |
| Content | Size | 3/8" IMPACT SOCKET | • | • | • | • | • | • | • | • | • | • | • |



MET-2305 Impact set 3/8" 11 pieces deep

Sockets

| Content | Size | METRIC (MM) | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 21 |
|---------|---------------|-------------------------|------|-------|-----|------|-------|-----|-------|-------|-----|-------|----|
| | INCH (SAE AF) | 3/8 | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 13/16 | |
| Content | Size | 3/8" IMPACT SOCKET DEEP | • | • | • | • | • | • | • | • | • | • | • |



MET-2400 Impact set 1/2" 15 pieces

Sockets

| Content | Size | METRIC (MM) | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 |
|---------|---------------|--------------------|-------|-----|------|-------|-----|-------|-------|-----|-------|-------|-----|-------|-------|----|----|
| | INCH (SAE AF) | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 25/32 | 13/16 | 7/8 | 29/32 | 15/16 | 1 | |
| Content | Size | 1/2" IMPACT SOCKET | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • |



MET-2450 Impact set 1/2" 15 pieces deep

Sockets

| Content | Size | METRIC (MM) | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 |
|---------|---------------|-------------------------|-------|-----|------|-------|-----|-------|-------|-----|-------|-------|-----|-------|-------|----|----|
| | INCH (SAE AF) | 7/16 | 15/32 | 1/2 | 9/16 | 19/32 | 5/8 | 11/16 | 23/32 | 3/4 | 25/32 | 13/16 | 7/8 | 29/32 | 15/16 | 1 | |
| Content | Size | 1/2" IMPACT SOCKET DEEP | • | • | • | • | • | • | • | • | • | • | • | • | • | • | • |



MET-2460 Impact Wheelnut set 1/2" 6 pieces

Sockets

| Content | Size | METRIC (MM) | 17 | 19 | 21 |
|---------|---------------|-------------------------|-----|-------|----|
| | INCH (SAE AF) | 1 1/16 | 3/4 | 13/16 | |
| Content | Size | 1/2" SOCKETS | • | • | • |
| Content | Size | 1/2" IMPACT SOCKET DEEP | • | • | • |

The background of the entire page features a diamond plate metal texture with a light beige or silver color.

METRINCH®