

## Positive Voltage Regulators

### GENERAL DESCRIPTION

The XC6201 series are highly precise, low power consumption, positive voltage regulators manufactured using CMOS and laser trimming technologies.

The series provides large currents with a significantly small dropout voltage.

The XC6201 consists of a current limiter circuit, a driver transistor, a precision reference voltage and an error amplifier. Output voltage is selectable in 0.1V steps between 1.3V ~ 6.0V.

SOT-25, SOT-89, USP-6B and TO-92 packages are available.


### APPLICATIONS

Smart phones / Mobile phones  
Portable game consoles  
Digital still cameras / Camcorders  
Digital audio equipment  
Reference voltage sources  
Multi-function power supplies

### FEATURES


<b>Maximum Output Current</b>	: 250mA (TYP.)
<b>Dropout Voltage</b>	: 0.16V @ 100mA : 0.40V @ 200mA
<b>Maximum Operating Voltage</b>	: 10V
<b>Output Voltage Range</b>	: 1.3V ~ 6.0V (0.1V increments)
<b>Fixed Voltage Accuracy</b>	: $\pm 1\%$ ( $V_{OUT(T)} \geq 2.0V$ ) $\pm 2\%$
<b>Low Power Consumption</b>	: 2.0 $\mu A$ (TYP.)
<b>Operating Ambient Temperature</b>	: -40 ~ 85
<b>Packages</b>	: SOT-25, SOT-89 TO-92 USP-6B
<b>Environmentally Friendly</b>	: EU RoHS Compliant, Pb Free
<b>Tantalum or Ceramic Capacitor compatible</b>	

### TYPICAL APPLICATION CIRCUIT




### TYPICAL PERFORMANCE CHARACTERISTICS

Supply Current vs. Input Voltage



## PIN CONFIGURATION



\*The dissipation pad for the USP-6B package should be solder-plated in recommended mount pattern and metal masking so as to enhance mounting strength and heat release. If the pad needs to be connected to other pins, it should be connected to the VSS (No.5) pin.

## PIN ASSIGNMENT

PIN NUMBER			PIN NAME	FUNCTION
SOT-25	SOT-89/TO-92 (T)	USP-6B		
5	1	3	VOUT	Output
2	2	5	VSS	Ground
1	3	1	VIN	Power Input
3, 4	-	2,4,6	NC	No Connection

## PRODUCT CLASSIFICATION

### Ordering Information


X C 6 2 0 1 P - (\*)  
↑ ↑

DESIGNATOR	ITEM	SYMBOL	DESCRIPTION
	Product Number	01	-
	Type of Regulator	P	3-pin regulator
	Output Voltage	13 ~ 60	e.g. 30:3.0V 50:5.0V
	Output Voltage Accuracy	1	± 1%
		2	± 2%
-	Packages (Order Unit)	MR	SOT-25 (3,000/Reel)
		MR-G	SOT-25 (3,000/Reel)
		PR	SOT-89 (1,000/Reel)
		PR-G	SOT-89 (1,000/Reel)
		TH	TO-92 Taping Type: Paper type (2,000/Tape)
		TH-G	TO-92 Taping Type: Paper type (2,000/Tape)
		TB	TO-92 Taping Type: Bag (500/Bag)
		TB-G	TO-92 Taping Type: Bag (500/Bag)
		DR	USP-6B (3,000/Reel)
		DR-G	USP-6B (3,000/Reel)

(\*1) The “-G” suffix denotes Halogen and Antimony free as well as being fully EU RoHS compliant.

\* ±1% accuracy can be set at  $V_{OUT(T)} \geq 2.0V$ .

## BLOCK DIAGRAM



## ABSOLUTE MAXIMUM RATINGS

T<sub>a</sub> = 25

PARAMETER		SYMBOL	RATINGS	UNITS
Input Voltage	VIN		12.0	V
Output Current	I <sub>OUT</sub>		500	mA
Output Voltage	V <sub>OUT</sub>		V <sub>SS</sub> -0.3 ~ V <sub>IN</sub> +0.3	V
Power Dissipation	SOT-25	P <sub>d</sub>	250	mW
	SOT-89		500	
	TO-92		300	
	USP-6B		120	
Operating Temperature	T <sub>OPR</sub>		-40 ~ +85	
Storage Temperature	T <sub>STG</sub>		-55 ~ +125	

## ELECTRICAL CHARACTERISTICS

XC6201P132      V<sub>OUT(T)</sub>=1.3V <sup>(\*)1</sup>

T<sub>a</sub>=25

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V <sub>OUT(E)</sub> <sup>(*)2</sup>	V <sub>IN</sub> =2.3V I <sub>OUT</sub> =10mA	1.274	1.300	1.326	V	
Maximum Output Current	I <sub>OUTmax</sub>	V <sub>IN</sub> =2.3V V <sub>OUT(E)</sub> 1.17V	60	-	-	mA	
Load Regulation	V <sub>OUT</sub>	V <sub>IN</sub> =2.3V 1mA I <sub>OUT</sub> 30mA	-	10	30	mV	
Dropout Voltage <sup>(*)3</sup>	V <sub>DIF1</sub>	I <sub>OUT</sub> =30mA	-	200	600	mV	
	V <sub>DIF2</sub>	I <sub>OUT</sub> =60mA	-	500	810		
Supply Current	I <sub>SS</sub>	V <sub>IN</sub> =2.3V	-	2.0	5.0	μA	
Line Regulation	$\frac{V_{OUT}}{V_{IN} - V_{OUT}}$	I <sub>OUT</sub> =10mA 2.3V V <sub>IN</sub> 10.0V	-	0.2	0.3	%/V	
Input Voltage	V <sub>IN</sub>		1.8	-	10	V	-
Output Voltage Temperature Characteristics	$\frac{V_{OUT}}{T_{OPR} - V_{OUT}}$	I <sub>OUT</sub> =40mA -40 T <sub>OPR</sub> 85	-	± 100	-	ppm/	

## ELECTRICAL CHARACTERISTICS (Continued)

XC6201P182 V<sub>OUT(T)</sub>=1.8V <sup>(\*)1</sup> Ta=25

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V <sub>OUT(E)</sub> <sup>(*)2</sup>	V <sub>IN</sub> =2.8V I <sub>OUT</sub> =40mA	1.764	1.800	1.836	V	
Maximum Output Current	I <sub>OUTmax</sub>	V <sub>IN</sub> =2.8V V <sub>OUT(E)</sub> 1.62V	80	-	-	mA	
Load Regulation	V <sub>OUT</sub>	V <sub>IN</sub> =2.8V 1mA I <sub>OUT</sub> 40mA	-	10	30	mV	
Dropout Voltage <sup>(*)3</sup>	V <sub>dif1</sub>	I <sub>OUT</sub> =40mA	-	200	370	mV	
	V <sub>dif2</sub>	I <sub>OUT</sub> =80mA	-	450	710		
Supply Current	I <sub>SS</sub>	V <sub>IN</sub> =2.8V	-	2.0	5.0	μA	
Line Regulation	$\frac{V_{OUT}}{V_{IN} - V_{OUT}}$	I <sub>OUT</sub> =40mA 2.8V V <sub>IN</sub> 10.0V	-	0.2	0.3	%/V	
Input Voltage	V <sub>IN</sub>		1.8	-	10	V	-
Output Voltage Temperature Characteristics	$\frac{V_{OUT}}{T_{opr} - V_{OUT}}$	I <sub>OUT</sub> =40mA -40 Topr 85	-	± 100	-	ppm/	

XC6201P272 V<sub>OUT(T)</sub>=2.7V <sup>(\*)1</sup> Ta=25

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V <sub>OUT(E)</sub> <sup>(*)2</sup>	V <sub>IN</sub> =3.7V I <sub>OUT</sub> =40mA	2.646	2.700	2.754	V	
Maximum Output Current	I <sub>OUTmax</sub>	V <sub>IN</sub> =3.7V V <sub>OUT(E)</sub> 2.43V	100	-	-	mA	
Load Regulation	V <sub>OUT</sub>	V <sub>IN</sub> =3.7V 1mA I <sub>OUT</sub> 60mA	-	15	40	mV	
Dropout Voltage <sup>(*)3</sup>	V <sub>dif1</sub>	I <sub>OUT</sub> =60mA	-	200	370	mV	
	V <sub>dif2</sub>	I <sub>OUT</sub> =120mA	-	450	710		
Supply Current	I <sub>SS</sub>	V <sub>IN</sub> =3.7V	-	2.0	5.0	μA	
Line Regulation	$\frac{V_{OUT}}{V_{IN} - V_{OUT}}$	I <sub>OUT</sub> =40mA 3.7V V <sub>IN</sub> 10.0V	-	0.2	0.3	%/V	
Input Voltage	V <sub>IN</sub>		1.8	-	10	V	-
Output Voltage Temperature Characteristics	$\frac{V_{OUT}}{T_{opr} - V_{OUT}}$	I <sub>OUT</sub> =40mA -40 Topr 85	-	± 100	-	ppm/	

## ELECTRICAL CHARACTERISTICS (Continued)

XC6201P332 V<sub>OUT(T)</sub>=3.3V <sup>(\*)1</sup>

Ta=25

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V <sub>OUT(E)</sub> <sup>(*)2</sup>	V <sub>IN</sub> =4.3V I <sub>OUT</sub> =40mA	3.234	3.300	3.366	V	
Maximum Output Current	I <sub>OUTmax</sub>	V <sub>IN</sub> =4.3V V <sub>OUT(E)</sub> 2.97V	150	-	-	mA	
Load Regulation	V <sub>OUT</sub>	V <sub>IN</sub> =4.3V 1mA I <sub>OUT</sub> 80mA	-	20	50	mV	
Dropout Voltage <sup>(*)3</sup>	V <sub>dif1</sub>	I <sub>OUT</sub> =80mA	-	200	360	mV	
	V <sub>dif2</sub>	I <sub>OUT</sub> =160mA	-	450	700		
Supply Current	I <sub>SS</sub>	V <sub>IN</sub> =4.3V	-	2.0	5.0	μA	
Line Regulation	$\frac{V_{OUT}}{V_{IN} - V_{OUT}}$	I <sub>OUT</sub> =40mA 4.3V V <sub>IN</sub> 10.0V	-	0.2	0.3	%/V	
Input Voltage	V <sub>IN</sub>		1.8	-	10	V	-
Output Voltage Temperature Characteristics	$\frac{V_{OUT}}{T_{OPR} - V_{OUT}}$	I <sub>OUT</sub> =40mA -40 Topr 85	-	± 100	-	ppm/	

XC6201P502 V<sub>OUT(T)</sub>=5.0V <sup>(\*)1</sup>

Ta=25

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS	CIRCUIT
Output Voltage	V <sub>OUT(E)</sub> <sup>(*)2</sup>	V <sub>IN</sub> =6.0V I <sub>OUT</sub> =40mA	4.900	5.000	5.100	V	
Maximum Output Current	I <sub>OUTmax</sub>	V <sub>IN</sub> =6.0V V <sub>OUT(E)</sub> 4.57V	200	-	-	mA	
Load Regulation	V <sub>OUT</sub>	V <sub>IN</sub> =6.0V 1mA I <sub>OUT</sub> 100mA	-	30	70	mV	
Dropout Voltage <sup>(*)3</sup>	V <sub>dif1</sub>	I <sub>OUT</sub> =100mA	-	160	340	mV	
	V <sub>dif2</sub>	I <sub>OUT</sub> =200mA	-	400	600		
Supply Current	I <sub>SS</sub>	V <sub>IN</sub> =6.0V	-	2.0	6.0	μA	
Line Regulation	$\frac{V_{OUT}}{V_{IN} - V_{OUT}}$	I <sub>OUT</sub> =40mA 6.0V V <sub>IN</sub> 10.0V	-	0.2	0.3	%/V	
Input Voltage	V <sub>IN</sub>		1.8	-	10	V	-
Output Voltage Temperature Characteristics	$\frac{V_{OUT}}{T_{OPR} - V_{OUT}}$	I <sub>OUT</sub> =40mA -40 Topr 85	-	± 100	-	ppm/	

NOTE:

\*1: V<sub>OUT(T)</sub> = Nominal output voltage.


\*2: V<sub>OUT(E)</sub> = Effective output voltage (i.e. the output voltage when "V<sub>OUT(T)</sub>+1.0V" is provided while maintaining a certain I<sub>OUT</sub> value).

\*3: V<sub>dif</sub> = (V<sub>IN1</sub>- V<sub>OUT1</sub>)

V<sub>IN1</sub> : An Input Voltage when V<sub>OUT1</sub> appears as the input voltage is gradually decreased.


V<sub>OUT1</sub> : A voltage equal to 98% of the output voltage when a stabilized (V<sub>OUT(T)</sub> + 1.0V) is input.

## TYPICAL APPLICATION CIRCUIT




With the XC6201 series regulator, in order to ensure the stabilized output voltage, we suggest that an output capacitor ( $C_L$ ) of 1  $\mu$  F or more be connected between the output pin (VOUT) and the Vss pin. For using low ESR capacitor (e.g. ceramic capacitors), please make sure that the output voltage is more than 1.7V. When the output voltage is from 1.3V to 1.6V, the output capacitor should be a tantalum capacitor with a capacitance of 2.2  $\mu$  F. We also suggest an input capacitor ( $C_{IN}$ ) should be connected between the VIN and the Vss in order to stabilize input power source.

OUTPUT VOLTAGE	$C_{IN}$	$C_L$ (TANTALUM)	$C_L$ (LOW ESR)
1.3V ~ 1.6V	1.0 $\mu$ F	2.2 $\mu$ F	-
1.7V ~ 6.0V	1.0 $\mu$ F	1.0 $\mu$ F	1.0 $\mu$ F




## TEST CIRCUITS

Circuit 1 : Supply Current



Circuit 2 : Output Voltage, Oscillation, Line Regulation, Dropout Voltage, Load Regulation








## NOTE ON USE

1. Please use this IC within the stated absolute maximum ratings. The IC is liable to malfunction should the ratings be exceeded. When a voltage higher than the  $V_{IN}$  flows to the  $V_{OUT}$  like when using two power supplies, please connect a Schottky barrier diode between the  $V_{OUT}$  and the  $V_{IN}$  and do not exceed the  $V_{OUT}$  rating.
2. An oscillation may occur by the impedance between a power supply and the input of the IC. Where the impedance is 10 or more, please use an input capacitor ( $C_{IN}$ ) of at least 1  $\mu$ F. In case of high output current, operation can be stabilized by increasing the input capacitor value. Also an oscillation may occur if the input capacitor value is smaller than the input impedance when the output capacitance ( $C_L$ ) is large. In such cases, operations can be stabilized by either increasing the input capacitor value or reducing the output capacitor value.
3. Please ensure that output current ( $I_{OUT}$ ) is less than  $P_d / (V_{IN} - V_{OUT})$  and do not exceed the rated power dissipation value ( $P_d$ ) of the package.







## TYPICAL PERFORMANCE CHARACTERISTICS

### (1) Output Voltage vs. Output Current







## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (2) Output Voltage vs. Input Voltage








## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (2) Output Voltage vs. Input Voltage (Continued)









## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (3) Dropout Voltage vs. Output Current







## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (4) Supply Current vs. Input Voltage




## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (4) Supply Current vs. Input Voltage (Continued)



## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)


### (5) Output Voltage vs. Ambient Temperature




## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (6) Supply Current vs. Ambient Temperature


XC6201P132




XC6201P182




XC6201P272



XC6201P332




XC6201P502




## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (7) Input Transient Response


XC6201P132




XC6201P182




XC6201P272



XC6201P332








XC6201P502





## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (8) Load Transient Response




## TYPICAL PERFORMANCE CHARACTERISTICS (Continued)

### (9) Ripple Rejection Rate




### (10) Output Noise Density



## PACKAGING INFORMATION


SOT-25

Unit : mm



SOT-89


Unit : mm




## PACKAGING INFORMATION (Continued)

TO-92



Paper type



Unit : mm





Bag




USP-6B

Unit : mm




## PACKAGING INFORMATION (Continued)

USP-6B Reference Pattern Layout




USP-6B Reference Metal Mask Design



## MARKING RULE

SOT-89, SOT-25




SOT-89  
(TOP VIEW)

represents the product series

MARK		PRODUCT SERIES	
1		XC6201xxxxx	

represents type of regulator

MARK		PRODUCT SERIES	
Voltage= 0.1 ~ 3.0V	Voltage= 3.1 ~ 6.0V	XC6201PXXXXX	
5	6		
8	9		XC6201TXXXPX



SOT-25  
(TOP VIEW)

represents output voltage


MARK	OUTPUT VOLTAGE (V)		MARK	OUTPUT VOLTAGE (V)		
0	-	3.1	-	F	1.6	4.6
1	-	3.2	-	H	1.7	4.7
2	-	3.3	-	K	1.8	4.8
3	-	3.4	-	L	1.9	4.9
4	-	3.5	-	M	2.0	5.0
5	-	3.6	-	N	2.1	5.1
6	-	3.7	-	P	2.2	5.2
7	-	3.8	-	R	2.3	5.3
8	-	3.9	-	S	2.4	5.4
9	-	4.0	-	T	2.5	5.5
A	-	4.1	-	U	2.6	5.6
B	-	4.2	-	V	2.7	5.7
C	1.3	4.3	-	X	2.8	5.8
D	1.4	4.4	-	Y	2.9	5.9
E	1.5	4.5	-	Z	3.0	6.0

represents assembly lot number

0 to 9, A to Z repeated (G, I, J, O, Q, W excluded)

## MARKING RULE (Continued)

TO-92



represents type of regulator

MARK	PRODUCT SERIES	
P	XC6201Pxxxx	
T	XC6201Txxxx	

represents output voltage

MARK	VOLTAGE (V)	PRODUCT SERIES
3	3	XC6201Px33xx
5	0	XC6201Px50xx

represents detect voltage accuracy

MARK	DETCT VOLTAGE ACCURACY	PRODUCT SERIES
1	Within $\pm 1\%$	XC6201Pxx1xx
2	Within $\pm 2\%$	XC6201Pxx2xx

represents least significant digit of production year


MARK	PRODUCTION YEAR	
3	2003	
4	2004	

represents the production lot number

0 to 9, A to Z repeated (G, I, J, O, Q, W excluded)

Note: No character inversion used.

USP-6B



represents product series

MARK	PRODUCT SERIES	
0	1	XC6201xxxxDx

represents type of regulator

MARK	TYPE	PRODUCT SERIES
P	3pin Regulator	XC6201PxxxDx
T	VIN=7V(Rated)	XC6201TxxxDx

represents output voltage

MARK	VOLTAGE (V)	PRODUCT SERIES
3	3	XC6201x33xDx
5	0	XC6201x50xDx

represents assembly lot number

0 to 9, A to Z repeated (G, I, J, O, Q, W excluded)

Note: No character inversion used.

1. The products and product specifications contained herein are subject to change without notice to improve performance characteristics. Consult us, or our representatives before use, to confirm that the information in this datasheet is up to date.
2. We assume no responsibility for any infringement of patents, patent rights, or other rights arising from the use of any information and circuitry in this datasheet.
3. Please ensure suitable shipping controls (including fail-safe designs and aging protection) are in force for equipment employing products listed in this datasheet.
4. The products in this datasheet are not developed, designed, or approved for use with such equipment whose failure of malfunction can be reasonably expected to directly endanger the life of, or cause significant injury to, the user.  
(e.g. Atomic energy; aerospace; transport; combustion and associated safety equipment thereof.)
5. Please use the products listed in this datasheet within the specified ranges. Should you wish to use the products under conditions exceeding the specifications, please consult us or our representatives.
6. We assume no responsibility for damage or loss due to abnormal use.
7. All rights reserved. No part of this datasheet may be copied or reproduced without the prior permission of TOREX SEMICONDUCTOR LTD.

**TOREX SEMICONDUCTOR LTD.**