



Ø30 Series

Control Units



IDEC IZUMI CORPORATION

Ø30 Ø30 Series Control Units (Selection Guide)

Function	Emergency Stop Switch				Pushl	outton			
Category	Pushlock Turn Reset	Flu	Flush Extended		nded		ed with Shroud	Extend Full S	ed with hroud
					Momentary	/Maintained			
Shape			C		0 N		O.N.		
	. (U) ∪s (D) (€	UL SEE C	€	UL OF C	€	Un OF C	€	UL GP C	€
Туре	HN1E	ABN1 AON1	(Diecast) ABD1 AOD1	ABN2 AON2	(Diecast) ABD2 AOD2	ABN2G AON2G	(Diecast) ABGD2 AOGD2	ABN2F AON2F	(Diecast) ABFD2 AOFD2
Page	6	13	69	13	69	13	69	13	69

Function					Pushl	outton				
Category	Mushroom		Mushroom with Full Shroud		Palm Mushroom		Jumbo Mushroom with Shallow Shroud		Jumbo Mus Deep S	
		Momentary	/Maintained				Mome	entary		
Shape			₩ @ (€				(h) (f) (f		(h) (f) (f)	
	ABN3	(Diecast)	usies -	(Diecast)	Listes		Listed			(Discost)
Туре	AON3	ABD3 AOD3	ABN3G	ABGD3 AOGD3	ABN4	(Diecast) ABD4	ABN4G	(Diecast) ABGD4	ABN4F	(Diecast) ABFD4
Page	14	70	14	70	14	70	14	70	14	70

Function			Pushl	outton			
Category	Square Flush	Square Extended	Mushroom Pushlock		Mushroom Pushlock	Jumbo Mushroom	
Category	Momentary	Momentary	Turn	Reset	Key Reset	Pushlock Key Reset	
Shape						G G	
	⊕ ⊕ (€		ULISTED (B)		LISTED (S)		
Туре	UBQN1	UBQN2	AVN3	(Diecast) AVD3	ABN3K	ABN4K	
Page	14 14		15	71	15	15	

Function				Pushbutton				
Category	Mushroom Push Turn Lock		Key ON/OFF Lock	Toggle Lever	Mushro	om Pull	Mushroom	Push-Pull
Shape	Shape							
	UL USTED GO C	€	⊕ ⑤ (€	(U _L) (S) ← (€	UL GO C	€	UL STED	
Туре	AJN3 (Diecast) AJD3		ABN5	ATN4	ATN23	(Diecast) AZD3	ATN21 ATN22	(Diecast) AYD3
Page	15 71		15	15	16	71	16	71

ø30 Series Control Units (Selection Guide) Ø

Function			Pushbutton		Twin Maintain	ed Pushbutton
Category	Din I	Lock	Square Twin	Square Twin	Flush	Mushroom
Category	I III LOCK		Momentary	Maintained	FluSii	Musificom
Shape			O N OFF	O N OFF	O	
	UL GF (€	(4) (3) (€	⊕ ⊕ (€	⊕ ⊕ (€	⊕ ⊕ (€
Туре	ABN8P	(Diecast) ABD8P	UWQN1	UWQN2	ABBN11	ABBN33
Page	16 71 17 17		17	17	17	

Function			Pilot Light (LED)		F	Pilot Light (Ir	ncandescent	:)
Category	Do	me	Square	Rectangular (Marking)	Dome (1W)		Dome (2W)	
Shape	Shape							
	(h) (B) (€	Un GP C E	<u>(I)</u> (B) (€	UL GP (€	UL GP (€
Туре	APN1 (Diecast) APNE1 APD1 APDE1		UPQN3B	UPQN4 UPQNE4	APN1	(Diecast) APD1	APN1 APNE1	(Diecast) APD1 APDE1
Page	18	72	19	19	19	72	18	72

Function	F	Pilot Light (Incandescent	t)	IIIu	ıminated Pu	shbutton (LED)
Category	Rectangular (Marking) (1W/2W)	Square Flush (1W)	Dome	Exte	nded	Extended with Half Shroud
	(100/200)		Push-to-Check		Momentary	/Maintained
Shape			(h) (f) (f)	(h) (f) (
	USTED W C C	LISTED & C	LISTED CO.	HOLES		LIOTES
Туре	UPQN4 UPQNE4 UPQN3B		APN1*P	ALN2 ALNE2 AOLN2 AOLNE2	(Diecast) ALD2 AOLD2	ALGN2 ALGNE2 AOLGN2 AOLGNE2
Page	19	19	21	22	73	24

Function			Illu	minated Pu	shbutton (LE	D)		(Incand	escent)
Category	Extended with Full Shroud		Mush	room	Mushroom Pushlock Turn Reset		Mushroom Push Turn Lock	Exte	nded
		Momentary	/Maintained		Turn	Reset	Turn Lock	Momentary	/Maintained
Shape	⊕⊕⊕⊕⊕						(h) (f) (€		
	maien — -		LISTED		UL STED SP		LISTED CO.	UL OF C	
Туре	ALFN2 ALFNE2 AOLFN2 AOLFNE2 (Diecast) ALFD2 AOLFD2		ALN3 ALNE3 AOLN3 AOLNE3	(Diecast) ALD3 AOLD3	AVLN3 AVLNE3 (Diecast) AVLD3 AVLDE3		AJLN3	ALN ALNE AOLN AOLNE	(Diecast) ALD2 AOLD2
Page	26	74	28	75	31	76	31	23	73

Ø30 Ø30 Series Control Units (Selection Guide)

Function			Illumina	ted Pushbutton (Incand	escent)	
Category	Extended with Half Shroud		Extended with Square Flush		Rectangular	Turn Lock
	Momentary		Momentary	/Maintained	Momentary/Maintained	
Shape						
	LISTED	2012		LISTED	LISTED	USTED 3
Туре	ALN*G ALNE3G3	ALN*F ALNE3F3 AOLN*F AOLNE3F3	(Diecast) ALFD2 AOLFD2	ULQN UOLQN	ULQN*B UOLQN*B	ALN*L
Page	25	27	74	29	29	30

Function	Illumina	ated Pushbu	tton (Incandescent)			Selecto	r Switch			
Category	Mushroom Turn l	n Pushlock Reset	Mushroom Push Turn Lock	Kr	Knob		Lever		Key	
Shape			The state of the s				0			
	UL STED		(U _L) (S∰. (€	UL STED C	€	UL GF C	€	UL STED	€	
Туре	AVLN3 (Diecast) AVLNE3 AVLD3 AVLDE3		AJLN3	ASN ASTN	(Diecast) ASD	ASN*L ASTN*L	(Diecast) ASD*L	ASN*K ASTN*K	(Diecast) ASD*K	
Page	32	76	32	33/37	77	34/38	78	35/39	79	

Function	Illuminate Switch		Illuminate Switch (Inc	d Selector andescent)		Selector Pushbutton			Mono-Lever Switch	
Category	Kn	ob	Knob Ring Lever		Standard					
Shape	Shape					a 49		O		
		€	UL GP (€	UL BYED (ϵ	UL OF C	€	UISTED (S)	
Туре	ASLN	(Diecast) ASLD	ASLN	(Diecast) ASLD	ABN	(Diecast) ASBD2	ABN*L	(Diecast) ASBD2L	ARN ARNS	
Page	40	80	40	80	42	82	42	82	44	

Function	Mono-Lever Switch	Cam Switch				
Category	Interlocking	Knob	Key	Maintained/ Spring Return	Spring Return	
Shape	The second					
	UISTED SP.	ULBTED SP.	ULSTED SP.	ULUSTED SP.	UL STED	
Туре	ARNL	ACSNO ACSSO	ACSNK ACSSK	UCSQO	UCSQM	
Page	44	47	47	47	47	

ø30 HN Series Emergency Stop Switches

Emergency Stop Switches (Unibody Type) Specifications

Contact Ratings

Rated Insula	tion Volt	250V			
Rated Therm	nal Curre	10A			
Rated Opera	24V	110V	220V		
Rated Operational Current	AC 50/60	Resistive Load (AC-12)	6A	ЗА	ЗА
	Hz	Inductive Load (AC-15)	6A	ЗА	ЗА
	DC	Resistive Load (DC-12)		2A	1A
		Inductive Load (DC-13)	1.5A	0.3A	0.15A

Note: The operational current represents the classification by making and breaking currents (IEC 60947-5-1).

Minimum applicable load (reference value): 3V AC/DC, 5 mA (Applicable range may vary with operating conditions and load types.)

LED Lamp Ratings

Unit Rated			LED Lamp	
	Operating Voltage	Type No.	Rated Voltage	Rated Current
	24V AC/DC	LSTD-2R	24V AC/DC ±10%	10 mA

Incandescent Lamp Ratings

Unit Rated	Incandescent Lamp		
Operating Voltage	Type No.	Wattage	
24V AC/DC	LS-3	1W (30V)	

Specifications

Operating	-25 to +60°C (no free	ezing)
Temperature	Illuminated units: -25	i to +55°C
Storage Temperature	-40 to +80°C	
Operating Humidity	45 to 85% RH (no co	ndensation)
Contact Resistance	50 mΩ maximum (ini	tial value)
Insulation Resistance	100 MΩ minimum (50	00V DC megger)
	Between live and dea	ad metal parts
Dielectric Strength	Contacts:	2,500V AC, 1 minute
	Illuminated parts:	1,000V AC, 1 minute
	Damage limits:	60 m/s ²
Vibration Resistance	Operating extremes:	
		amplitude 0.5 mm
Shock Resistance	Damage limits:	1,000 m/s ²
SHOCK IVESISIANCE	Operating extremes:	100 m/s ²
Operating Frequency	900 operations/h	
Life	Mechanical: 250,00	00 operations minimum
LIIE	Electrical: 100,00	00 operations minimum
Degree of Protection	IP65	
Terminal Style	M3.5 screw	

Applicable Standards and Approvals

Safety Standards	File No. or Organization
UL508	UL Listing File No. E55996
CSA C22.2 No. 14	c-UL (File No. E55996)
EN60947-5-5	DEMKO approved

Pushlock Turn Reset Switches (Unibody Type)

Shape	Contact	Type No.	Button Color
	1NO-1NC	HN1E-BV411R	- Red only
c	2NC	HN1E-BV402R	Red Only

- When pressed, the button is held depressed. The button is released by turning clockwise.
- Terminal cover HW-VL7 is supplied with the switch.

Illuminated Pushlock Turn Reset Switches (Unibody Type)

Shape	Lamp	Contact	Type No.	Lens Color
	Without Lamp	1NO-1NC	HN1E-LV411Q0R	- Red only
c	without Lamp	2NC	HN1E-LV402Q0R	Neu only

- When pressed, the button is held depressed. The button is released by turning clockwise.
- The illuminated pushlock turn reset switch does not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- Terminal cover HW-VL7 is supplied with the switch.

ø30 HN Series Emergency Stop Switches

Dimensions Panel Cut-Out • HN1E-BV4 M3.5 Terminal Screw R0.8 max. Panel Thickness 0.8 to 6 4.8 0 0 33 Terminal Arrangement (Bottom View) TOP Marking Side Locking Ring .4(NO) • HN1E-LV4 Panel Thickness 0.8 to 6 Terminal Arrangement (Bottom View) TOP Marking Side Lamp Terminal Locking Ring All dimensions in mm.

Replacement Parts

Name	Type No.	Ordering Type No.	Package Quantity	Remarks
Terminal Cover	HW-VL7	HW-VL7PN10	10	Used on HN1E emergency stop switches for preventing electrical shocks. The HW-VL7 terminal cover is supplied with the HN1E.

Nameplates

Shape	Type No.	Legend	Package Quantity	Remarks
WIERGENCL	HNAV-0	(blank)	1	Background: Yellow Legend: Black Applicable panel thickness: 0.8 to 4.5 mm Material: Polyamide
\$108	HNAV-27	EMERGENCY STOP	1	Legend "EMERGENCY STOP" is indicated outside a Ø44mm circle.

Accessory

Shape	Material	Type No.	Package Quantity	Remarks	
	Metal	TWST-T1	1	Used for tightening the locking nut. Tighten the locking nut to a torque of 2.0 to 2.5 N·m.	23.7 77 77 77 78 78 78 78 78 78 78 78 78 78

ø30 ø30 Series Control Units

Heavy duty control units offer both variety and reliability

- **Endures harsh environments**
- Degree of protection: IP65 • UL, CSA approved, and EN compliant.

Safety	y Standards	File No. or Organization
UL	(JL)	UL Listing File No. E68961

CSA

File No. LR21451

EN EN60947-5-1



Specifications and Ratings

Contact Ratings

Pushbuttons	Contact Block	Type BS/BST (ø30 series)
Illuminated Pushbuttons	Rated Insulation Voltage	600V
Selector Switches	Rated Continuous Current	10A
 Illuminated Selector Switches	Contact Ratings by Utilization Category	AC-15 (A600)
Selector Pushbuttons	IEC 60947-5-1	DC-13 (P600)


Characteristics

Contact Ratings by Utilization Category

Operational Voltage				24V	48V	50V	110V	220V	440V
	AC		Control of resistive loads and solid state loads	10A	_	10A	10A	6A	2A
Operational 50/60 Hz	AC-15	Control of electromagnetic loads (> 72 VA)	10A	_	7A	5A	3A	1A	
Current	DC	DC-12	Control of resistive loads and solid state loads	10A	5A	_	2.2A	1.1A	_
	DC	DC-13	Control of electromagnets	5A	2A	_	1.1A	0.6A	_

Note: The operational current represents the classification by making and breaking currents (IEC 60947-5-1). Minimum applicable load: 3V AC/DC, 5 mA (applicable range may vary with operating conditions and load types) For mono-levers and cam switches, see pages 43 and 46.

BS (BST) Contact Block



Contact Block Types

		Single-pole Contact Block Type				
Contact						
		1NO	1NC	1NO (early make)	1NC (late break)	
Time	BS	BS010E	BS001E	BS010SE	BS001SE	
Туре	BST	BST010	BST001	BST010S	BST001S	
Push Rod		Green	Red	Black	White	

BST contact blocks are used for the following control units and are not interchangeable with BS contact blocks.

(The BS housing is dark gray and the BST housing is light gray.)

- Pushlock turn reset and push turn lock switches
- LED illuminated pushbuttons
- LED/incandescent illuminated selector switches
- All models of diecast zinc housing control units
- Durable nylon 66 housing has a high resistance against alkalis.
- · Silver contacts.
- Up to four blocks in two layers can be mounted onto each operator.

LED Illuminated Unit Specifications

Unit	Color Code ② Input		Input Type	Type Operating Voltage		LED Lamp			
J Olin		noi code ©	iliput Type	Operating voltage	Lamp Base	Type No.	Voltage		
				6V AC/DC		LSTD-62	6V AC/DC ±10%		
				12V AC/DC	BA9S/13	LSTD-12	12V AC/DC ±10%		
			Full Voltage	24V AC/DC		LSTD-2®	24V AC/DC ±10%		
			Full voltage	6V AC/DC		LETD-62	6V AC/DC ±10%		
				12V AC/DC	E12/15	LETD-82	12V AC/DC ±10%		
	1			24V AC/DC		LETD-22	24V AC/DC ±10%		
Pilot Light Illuminated Pushbutton Illuminated Selector Switch		PW: pure white R: red S: blue N: white	Transformer	100/110V AC/DC 115V AC/DC 120V AC/DC 200/220V AC/DC	BA9S/13	LSTD-62			
		Transformer	230V AC/DC 240V AC/DC 380V AC/DC 400/440V AC/DC (50/60 Hz)	E12/15	LETD-62	- 6V AC/DC ±10%			
			DC-DC Converter	110V DC	BA9S/13	LSTD-62	6V AC/DC ±10%		
			DC-DC Converter	TIOV DC	E12/15	LETD-62	0 V AC/DC ±10%		

Incandescent Illuminated Unit Specifications

Unit	Color Code 2	Innut Type	Innut Type Operating Voltage		Incandescent Lamp		
Unit	Color Code 2	Input Type	Operating Voltage	Lamp Base	Type No.	Rating	
			6V AC/DC		LS-6	1W (6.3V)	
			12V AC/DC	BA9S/13	LS-8	1W (18V)	
		Full Voltage	24V AC/DC		LS-3	1W (30V)	
		ruii voitage	6V AC/DC		LE-6	2W (6.3V)	
			12V AC/DC	E12/15	LE-8	2W (18V)	
	A: amber G: green	24V AC/DC		LE-3	12W (30V)		
Pilot Light Illuminated Pushbutton Illuminated Selector Switch	O: orange R: red S: blue W: white Transfo	115V AC/DC 120V AC/DC 200/220V AC/D 230V AC/DC	120V AC/DC 200/220V AC/DC	BA9S/13	LS-6	1W (6.3V)	
		ITANSIOTHER	240V AC/DC 380V AC/DC 400/440V AC/DC 480V AC/DC (50/60 Hz)	E12/15	LE-8	2W (18V)	

LED Lamp Ratings (LSTD Type)

	inp itat	ings (LSTD Type)				
Type No.		LSTD-62 LSTD-12		LSTD-2②		
Lamp Base	е	BA9S/13	BA9S/13			
Rated Volt	age	6V AC/DC	12V AC/DC	24V AC/DC		
Voltage Ra	ange	6V AC/DC ±10%	12V AC/DC ±10%	24V AC/DC ±10%		
Current	AC	A, R, W, Y: 17 mA G, PW, S: 8 mA	11 mA	11 mA		
Draw	DC	A, R, W, Y: 14 mA G, PW, S: 5.5 mA	10 mA	10 mA		
Color Code	e ②	A (amber), G (green), PW (pure white), R	R (red), S (blue), W (v	vhite), Y (yellow)		
Lamp Base	e Color	Same as illumination color				
Voltage Ma	arking	Die stamped on the base				
Life (reference value)		Approx. 50,000 hours (The luminance is reduced to 50% the initial intensity when used on complete DC.)				
		A, R, W, Y		, W, Y		
Internal Ci	icuit	G, PW, S				
			LED Chip Protection Diode Zener Diode			

LED Lamp Ratings (LETD Type)

Type No.		LETD-6②	LETD-82	LETD-22		
Lamp Bas	е	E12/15				
Rated Volt	age	6V AC/DC	12V AC/DC	24V AC/DC		
Voltage Ra	ange	6V AC/DC ±10%	12V AC/DC ±10%	24V AC/DC ±10%		
Current	AC	A, R, W, Y: 17 mA G, S: 8 mA	7 mA	11 mA		
Draw	DC	A, R, W, Y: 14 mA G, S: 5.5 mA	6.5 mA	10 mA		
Color Cod	e ②	A (amber), G (green), R (red), S (blue), V	V (white), Y (yellow)			
Lamp Bas	e Color	Same as illumination color				
Voltage M	arking	Die stamped on the base				
Life (refere	ence value)	Approx. 50,000 hours (The luminance is reduced to 50% the initial intensity when used on complete DC.)				
		A, R, W, Y	A, R, W, Y			
Internal Circuit						
		G, S				
		LED Chip Protection Diode Zener Diode				

Incandescent Lamp Ratings (LS Type)

Type No.	LS-6	LS-8	LS-2	LS-3	
Lamp Base	BA9S/13			·	
Rated Voltage	6V AC/DC	12V AC/DC	18V AC/DC	24V AC/DC	
Wattage	1W (6.3V)	1W (18V)	1W (24V)	1W (30V)	
Voltage Marking	Die stamped on the	base	•	·	
Life (reference value)	Approx. 1,000 hours minimum (mean value when used on the rated voltage)				

Incandescent Lamp Ratings (LE Type)

	1 0 1 7							
Type No.	LE-6	LE-8	LE-2	LE-3				
Lamp Base	E12/15							
Rated Voltage	6V AC/DC	12V AC/DC	18V AC/DC	24V AC/DC				
Wattage	2W (6.3V)	2W (18V)	2W (24V)	2W (30V)				
Voltage Marking	Die stamped on the	Die stamped on the base						
Life (reference value)	Approx. 1,000 hours minimum							
Life (reference value)	(mean value when used on the rated voltage)							

ø30 ø30 Series Control Units

Specifications


Operating Temperature	-25 to +50°C (no freezing)				
Operating Humidity	45 to 85% RH (no condensation)				
Contact Resistance	,				
	50 mΩ maximum (initial value)				
Insulation Resistance	100 MΩ minimum (500V DC megger)				
Dielectric Strength	Between live and dead metal parts: 2,500V AC, 1 minute				
	(Full voltage type and pilot lights: 2,000V AC, 1 minute)				
Vibration Resistance	Operating extremes: 5 to 55 Hz, amplitude 0.5 mm				
Shock Resistance	Damage limits: 1,000 m/s ²				
Shock Resistance	Operating extremes: 100 m/s ²				
	Pushbuttons				
	Momentary: 5,000,000				
	Maintained: 500,000				
	Illuminated pushbuttons				
	Momentary: 2,500,000				
	Maintained: 500,000				
	Selector switches: 500,000				
Mechanical Life	Key selector switches: 500,000				
(minimum operations)	Illuminated selector switches: 500,000				
	Selector pushbuttons: 250,000				
	Mono-lever switches: 500,000				
	(Interlocking type): 250,000				
	Pushlock turn reset 500,000				
	Mushroom push-pull switch				
	Two contact blocks: 500,000				
	Four contact blocks: 200,000				
	Pushbuttons: 500,000 *1				
	Illuminated pushbuttons: 500,000 *1				
	Selector switches: 500,000 *2				
	Key selector switches: 500,000 *2 Illuminated selector switches: 500,000 *2				
	Selector pushbuttons: 250,000 *2				
Electrical Life	Mono-lever switches: 500,000 *3				
(minimum operations)	(Interlocking type): 250,000 *3				
, , ,	*1 Switching frequency 1,800 operations/h, duty ratio 40% *4				
	*2 Switching frequency 1,200 operations/h, duty ratio 40%				
	*3 Switching frequency 900 operations/h, duty ratio 40%				
	*4 Switching frequency 900 operations/h for square twin or twin maintained types				
	maintained types				

Degree of Protection

Type No.	Unit	NEMA ICS 6-110	IEC 60529
A****	Pushbuttons, pilot lights, illuminated pushbuttons, selector switches, selector pushbuttons, mono-lever switches, and cam switches (ACSNO/ACSSO)	Type 1, 2, 3, 3R, (3S), 4, 5, 12,13	IP65
A	Illuminated selector switches, key pushbuttons, key reset pushbuttons, key cam switches, and key selector switches	Type 1, 2, 3, 3R, 5, 12, 13	IP54
U****	Square pushbuttons, square pilot lights, and cam switches (UC)	Type 1, 2	IP40

Note: (3S) of NEMA ICS 6-110 applies to the pilot lights with round lens.

Mounting Hole Layout



*The minimum mounting centers are applicable to switches with one layer of contact blocks (two contact blocks). When two layers of contact blocks (four contact blocks) are mounted, determine the minimum mounting centers in consideration of convenience for wiring.

Mushroom with shroud:
 Jumbo mushroom:
 Jumbo mushroom with shroud:
 Square twin:
 Selector switch with lever:
 So mm minimum
 So mm minimum
 So mm minimum
 So mm minimum

☆ The 4.8 mm recess is for preventing rotation and is not necessary when the nameplate or anti-rotation ring is not used.

Note: For mounting hole layout of pushbuttons, mono-lever switches, and cam switches, see each section.

Ordering Information

Standard Units


- Specify an operator or lens color code in the Type No.
- · Black, green, and red buttons are included with flush push-
- Full voltage type illuminated units are not supplied with a lamp. Order LED or incandescent lamps separately. Transformer and DC-DC converter type illuminated units contain an LED or incandescent lamp.
- Terminal covers, nameplates, and accessories are ordered separately.

Terminal Cover

• When a terminal cover is required, order an applicable terminal cover referring to page 55.

The Type No. development charts shown below can be used to specify control units other than those listed on the following pages. Gold-plated silver contacts are also available.


ø30 Series Pushbuttons



Note:

- Mushroom pull type ATN23 can have a maximum of two contact
- Mushroom push-pull return type ATN22 cannot have only NO or only NC contacts.
- No other contact configurations are available for square twin type UWQN1 than those specified in this catalog.


ø30 Series Pilot Lights



Note:

- Full voltage type is not supplied with a lamp.
- Transformer and DC-DC converter types contain an LED lamp (LSTD-62) or LETD-62) or incandescent lamp (LS-6, 1W or LE-8,
- LED lamps cannot be used on 480V AC transformers.
- DC-DC converter is available with LED lamps only.
- Operating voltage codes 18, 118, 128, 28, 238, 248, 388, 48, and 488 are available for incandescent types only.

ø30 Series Illuminated Pushbuttons



Note:


- Illuminated pushbuttons cannot have an odd number of contact blocks, such as 1NO, 1NC, 3NO, 2NO-1NC, 1NO-2NC, and 3NC.
- Transformer and DC-DC converter types contain an LED lamp (LSTD-62) or LETD-62) or incandescent lamp (LS-6, 1W or LE-8,
- LED lamps cannot be used on 480V AC transformers.
- DC-DC converter is available with LED lamps only.
- Operating voltage codes 18, 118, 128, 28, 238, 248, 388, 48, and 488 are available for incandescent types only.

ø30 | ø30 Series Control Units (Ordering Information)

ø30 Series Selector Switch

ASN 2 L 11 - MAU Optional contact MAU: Gold-plated silver contact Contact arrangement code Operator type (blank): Knob Lever Number of positions


ø30 Series Key Selector Switch



Note:

• The key cannot be removed in the return position.

ø30 Series Illuminated Selector Switch



Note:

- Full voltage type is not supplied with a lamp.
- Transformer type contain an LED lamp (LSTD-62) or incandescent lamp (LS-6, 1W).
- LED lamps cannot be used on 480VAC transformers.

Flush / Extended / Extended w/Half Shroud / Extended w/Full Shroud Types

Shape	Operation Type	Contact	Type No.	① Button Color Code	Dimensions (mm)
Flush		1NO	ABN110①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
ABN1		1NC	ABN101①		
	Momentary	1NO-1NC	ABN111①	Black (B), green	
	Momentary	2NO	ABN120①	(G), and red (R)	6 23 40
		2NC	ABN102①	buttons are sup- plied with each	46 (1 or 2 blocks) 9
		2NO-2NC	ABN122①	unit.	69 (3 or 4 blocks)
Flush		1NO	AON110①	0	M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
AON1		1NC	AON101①	Specify Y or W when a yellow or	
	Maintained	1NO-1NC	AON111①	white button is	
	Mairitairieu	2NO	AON120①	required.	6 23
		2NC	AON102®		68 (1 to 2 blocks)
UL CLETED OF CE		2NO-2NC	AON122①		91 (3 to 4 blocks) 9
Extended		1NO	ABN210①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
ABN2		1NC	ABN201①		
	Momentary	1NO-1NC	ABN211①		
	wionicinary	2NO	ABN220①		6 23
		2NC	ABN202①		46 (1 or 9 2 blocks) 15.5
ULISTED GO C E		2NO-2NC	ABN2221		69 (3 or 4 blocks)
Extended		1NO	AON210①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
AON2		1NC	AON201®		
	Maintained	1NO-1NC	AON211①		
	Maintainea	2NO	AON220①		6 23
		2NC	AON202①		68 (1 to 2 blocks) 9 15.5
USTED (F		2NO-2NC	AON222①		91 (3 to 4 blocks)15.5
Extended with Half Shroud ABN2G		1NO	ABN2G10①		M3.5 Terminal Screw Panel Thickness 0.8 to 4
ADIVZG		1NC	ABN2G01①		
	Momentary	1NO-1NC	ABN2G11①	Specify a button color code in	
		2NO	ABN2G20①	place of ① in the Type No.	6 23 40
		2NC	ABN2G02①		42 (1 or 2 blocks) 20.5
UL STED GE C E		2NO-2NC	ABN2G22①	B: black	65 (3 or 4 blocks)
Extended with Half Shroud AON2G		1NO	AON2G10①	G: green	M3.5 Terminal Screw Panel Thickness 0.8 to 4
TIONES		1NC	AON2G01®	R: red W: white	
	Maintained	1NO-1NC	AON2G11①	Y: yellow	86 86 86 86 86 86 86 86 86 86 86 86 86 8
		2NO	AON2G20①		6 23
⊕ ⊕ (€		2NC	AON2G02®		64 (1 or 2 blocks) 87 (3 or 4 blocks) 20.5
Extended with Full Shroud		2NO-2NC	AON2G22①		
ABN2F		1NO 1NC	ABN2F10①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
0.1		1NO-1NC	ABN2F01① ABN2F11①		
	Momentary	2NO	ABN2F110	-	
		2NC	ABN2F02①	-	6 23 40 40
ULISTED GO C E		2NO-2NC	ABN2F22①	-	2 blocks) 17 69 (3 or 4 blocks)
Extended with Full Shroud		1NO	AON2F10①		
AON2F		1NC	AON2F100		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
0.0		1NO-1NC	AON2F010		88 S S S S S S S S S S S S S S S S S S
	Maintained	2NO	AON2F20①		
		2NC	AON2F02①		6 23 40 5 68 (1 or 2 blocks)
ULISTED SP. (E		2NO-2NC	AON2F02①		91 (3 or 4 blocks) 17
LISTED		2110-2110	AUNZI ZZU		

- Round bezel and shroud (metal): Chrome-plated
- Other contact arrangements and gold-plated silver contacts are also available. See page 11.

Mushroom / Jumbo Mushroom / Square Flush / Square Extended Types

Shape	Operation Type	Contact	Type No.	① Button Color Code	Dimensions (mm)
Mushroom		1NO	ABN310①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
ABN3		1NC	ABN301①		
		1NO-1NC	ABN311①		
	Momentary	2NO	ABN320①		6 23
		2NC	ABN302①		46 (1 or 2 blocks) 21
ULISTED GE CE		2NO-2NC	ABN3221		69 (3 or 4 blocks)
Mushroom		1NO	AON310①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
AON3		1NC	AON301®	B: black	
	Maintained	1NO-1NC	AON311①	G: green R: red	
	Mantanica	2NO	AON320①	W: white	6 23 40
		2NC	AON302®	Y: yellow	68 (1 or 2 blocks)
ULISTED (F		2NO-2NC	AON322①		91 (3 or 4 blocks) 21
Mushroom with Full Shroud ABN3G		1NO	ABN3G10①		M3.5 Terminal Screw Panel Thickness 0.8 to 6.5
ADING		1NC	ABN3G01®		
	Momentary	1NO-1NC	ABN3G11①		
	Womentary	2NO	ABN3G20①		6 23
		2NC	ABN3G02①		44 (1 or 2 blocks) 23
⊕ ⑤ (€		2NO-2NC	ABN3G22①		67 (3 or 4 blocks)
Palm Mushroom		1NO	ABN410①		M3.5 Terminal Screw
ABN4		1NC	ABN401①		
	Momentary	1NO-1NC	ABN411①		
al and a second	, momonium,	2NO	ABN420①		6 23
		2NC	ABN402①		2 blocks) 35
(I) (I) (I)		2NO-2NC	ABN422①		69 (3 or 4 blocks)
Jumbo Mushroom with Shallow Shroud		1NO	ABN4G10①		M3.5 Terminal Screw
ABN4G		1NC	ABN4G01①	D. block	
	Momentary	1NO-1NC	ABN4G11①	B: black G: green	
97	,	2NO	ABN4G20①	R: red	6 23 46 (1 or)
		2NC	ABN4G02①		46 (1 or 2 blocks) 28 69 (3 or 4 blocks)
ULISTED (F		2NO-2NC	ABN4G22①		
Jumbo Mushroom with Deep Shroud		1NO	ABN4F10①		M3.5 Terminal Screw
ABN4F		1NC	ABN4F01①		
	Momentary	1NO-1NC	ABN4F11①		
		2NO	ABN4F20①		46 (1 or
UL STED CE		2NC	ABN4F02®		69 (3 or 4 blocks)
Square Flush		2NO-2NC	ABN4F22①		
UBQN1		1NO 1NC	UBQN110① UBQN101①		M3.5 Terminal Screw Panel Thickness 0.8 to 5.5
		1NO-1NC	UBQN1010	-	
	Momentary	2NO	UBQN120①		
		2NC	UBQN102①		6 23 47.5 (1 or 40
₩ ()		2NO-2NC	UBQN122①	B: black	2 blocks) 14 44 70.5 (3 or 4 blocks)
Square Extended		1NO	UBQN210①	G: green R: red	
UBQN2		1NC	UBQN2100	Y: yellow	
		1NO-1NC	UBQN211①		13 A 1 A 1 A 1 A 1 A 1 A 1 A 1 A 1 A 1 A
	Momentary	2NO	UBQN220①	-	6 23
		2NC	UBQN202①	-	47.5 (1 or 40
⊕ ⊕ (€		2NO-2NC	UBQN222①		2 blocks) 20 70.5 (3 or 4 blocks)
nsien	<u> </u>	2110 2110	J D Q I 1222		,

- \bullet Specify a button color code in place of $\ensuremath{\textcircled{\scriptsize 1}}$ in the Type No.
- Round bezel and shroud (metal): Chrome-plated
- Other contact arrangements and gold-plated silver contacts are also available. See page 11.

Pushlock Turn Reset / Pushlock Key Reset / Push Turn Lock / **Key ON/OFF Lock / Toggle Lever Types**

Shape	Contact	Type No.	① Button Color Code	Dimensions (mm)			
Mushroom Pushlock Turn Reset	1NO	AVN310N®		M3.5 Terminal Screw _ Panel Thickness 0.8 to 7.5			
AVN3	1NC	AVN301N®					
	1NO-1NC	AVN311N①	R: red	9 () 8			
E 1 4	2NO	AVN320N®	Y: yellow	5.5 23 40			
	2NC	AVN302N®		53 (1 or 2 blocks) 24			
UL SP	2NO-2NC	AVN322N®		76 (3 or 4 blocks)			
Mushroom Pushlock Key Reset	1NO	ABN3K10①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5			
ABN3K	1NC	ABN3K01®	B: black				
	1NO-1NC	ABN3K11①	G: green				
	2NO	ABN3K20①	R: red	6 23 40			
	2NC	ABN3K02®	Y: yellow	53 (1 or 2			
UL LISTED	2NO-2NC	ABN3K22①		76 (3 or 4 blocks)			
Jumbo Mushroom	1NO	ABN4K10①		M3.5 Terminal Screw			
Pushlock Key Reset ABN4K	1NC	ABN4K01®		MISS TERMINIAL COLOR			
ABINAK	1NO-1NC	ABN4K11①	B: black G: green R: red				
	2NO	ABN4K20①					
	2NC	ABN4K02①		53 (1 or 2			
UL USTED	2NO-2NC	ABN4K22①		76 (3 or 4 blocks)			
Mushroom Push Turn Lock	1NO	AJN310N①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5			
AJN3	1NC	AJN301N①	B: black				
1 3 100	1NO-1NC	AJN311N①	G: green	8 8			
(a)	2NO	AJN320N①	R: red	5.5 23 40			
	2NC	AJN302N①	Y: yellow	53 (1 or 2 blocks) 24			
⊕ G€	2NO-2NC	AJN322N①		76 (3 or 4 blocks)			
Key ON/OFF Lock	1NO	ABN510		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5			
ABN5	1NC	ABN501		W3.5 Terminal Screw 90°			
	1NO-1NC	ABN511					
	2NO	ABN520	_	6 23			
	2NC	ABN502		54 (1 or 2 blocks) 23 23.5			
ULISTED (E	2NO-2NC	ABN522		77 (3 or 4 blocks)			
Toggle Lever	1NO	ATN410		M3.5 Terminal Screw Panel Thickness 0.8 to 5.5			
ATN4	1NC	ATN401					
	1NO-1NC	ATN411	Lever: black				
	2NO	ATN420	LOVOI. DIAGN	6 23			
	2NC	ATN402		44 (1 or 2 blocks) 25			
⊕ ⊕ (€	2NO-2NC	ATN422		67 (3 or 4 blocks)			

- Specify a button color code in place of ① in the Type No.
- Round bezel (metal): Chrome-plated
- Cylinder (metal): Chrome-plated
- Other contact arrangements and gold-plated silver contacts are also available. See page 11.
- Pushlock Turn Reset: Button is maintained when pressed and is reset when turned clockwise. Red buttons only.

Note: AVN3 pushlock turn reset switches cannot be used as emergency stop switches. When emergency stop switches are required, use the HN1E series emergency stop switches (ISO 13850 and IEC 60947-5-5 compliant).

- Pushlock Key Reset: Button is maintained when pressed and is reset with a key. Key is removable from both depressed and reset positions. Two keys are supplied.
- Push Turn Lock: Button is locked when turned clockwise in the depressed position and is reset when turned counterclockwise.
- Key ON/OFF Lock: Button can be locked in both depressed and reset positions.
- Toggle Lever: ON and OFF are indicated on the cap.

Pull / Push-Pull / Pin Lock Types

Shape	Contact	Type No.	① Button Color Code	Dimensions (mm)
Mushroom Pull ATN23	1NO	ATN2310①		M3.5 Terminal Screw - Panel Thickness 0.8 to 7.5
ATTV25	1NO-1NC	ATN2311①		88
	2NO	ATN2320①		6 23 40
U) SP (E	2NC	ATN2302①		53 (1 or 2 blocks) 38.5
Mushroom Push-Pull ATN21	1NO-1NC	ATN2111①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
	2NO	ATN2120①	B: black G: green	98
	2NC	ATN2102①	R: red Y: yellow	6 23 40 40 40 40 40 40 40 40 40 40 40 40 40
UN STED	2NO-2NC	ATN2122①		blocks) 38.5 76 (3 or 4 blocks)
Mushroom Push-Pull (Spring Return) ATN22	1NO-1NC	ATN2211①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
	2NO-2N C	ATN2222①		6 23 53 (1 or 2 blocks) 38.5 76 (3 or 4 blocks)
Pin Lock	1NO	ABN8P10		Panel Thickness 0.8 to 7.5
ABN8P	1NC	ABN8P01		M3.5 Terminal Screw
	1NO-1NC	ABN8P11		828 828 828 828 828 828 828 828 828 828
	2NO	ABN8P20	_	
	2NC	ABN8P02		44.5 (1 or 2 blocks) 26.5 49
(h) (h) (€	2NO-2NC	ABN8P22		67 (3 or 4 blocks)
Pin Lock (ON Lock Type)	1NO	ABN8P10-TK231-1		Panel Thickness 0.8 to 7.5
ABN8P** -TK231-1	1NC	ABN8P01-TK231-1		M3.5 Terminal Screw
-11/231-1	1NO-1NC	ABN8P11-TK231-1	_	33,5
	2NO	ABN8P20-TK231-1		6 23
	2NC	ABN8P02-TK231-1		44 (1 or 2 blocks) 25.4 40 49
USTED SP (E	2NO-2NC	ABN8P22-TK231-1		67 (3 or 4 blocks)

- Specify a button color code in place of ① in the Type No.
- Round bezel and shroud (metal): Chrome-plated
- Square bezel (metal): Chrome-plated
- Other contact arrangements and gold-plated silver contacts are also available. See page 11.
- Pull: Pulling the button operates the contacts. Up to 2 contact blocks (1 layer) can be mounted on pull switches.
- Push-Pull: Button is maintained in both depressed and reset positions.
- Push-Pull (Spring Return): Pushing or pulling the button operates the contacts. Button is spring-returned to the center position.
- Pin Lock: Button can be locked in either depressed or reset position by inserting the pin. Pad lock with a ø6mm pin can also be used to lock
- Pin Lock (ON Lock Type): Button is locked in the depressed position by inserting the pin. Button cannot be locked in the reset position.

Contact Operation

Pull Switch (Spring Return)

Contact	ATN23			
Contact	Normal	Pull		
1NO	9-0	- - -		
1NC	•	●1●		
1NO-1NC	ტ • ••	00 11		
2NO	99 99	1000 1000		
2NC	••• •••	616 616		

Push-Pull Switch (Maintained)

ATN21			
Push	Pull		
₼ ••	0 10		
مړه مړه	~ · · ·		
••• •••	616 616		
~ • • • • • • • • • • • • • • • • • • •	1 0 10		
	Push		

Push-Pull (Spring Return) Switch

		,	
Contact		ATN22	
Contact	Push	Normal	Pull
1NO-1NC	ტ <u>•</u> ••	~ · ·	<u></u>
2NO-2NC	↔ .	% +% •4.	% % % % % % % % % % % % % % % % % % %

Square Twin / Twin Maintained Types

Shape	Con	tact	Type No.	Button Color	Dimensions (mm)		
Square Twin (Momentary) UWQN1	ON	OFF					
OWQIVI	1NO	1NO	UWQN11010		M3.5 Terminal Screw Panel Thickness 0.8 to 13		
O N OFF	1NO	1NC	UWQN11001	ON: Black OFF: Red	6 23 47 (1 or 2 blocks) 15.5		
(f) (f) (€	2NO	2NC	UWQN12002		70 (3 or 4 blocks)		
Square Twin (Maintained)	ON	OFF					
UWQN2	1NO	-	UWQN21000		M3.5 Terminal Screw Panel Thickness 0.8 to 13		
	1NC	-	UWQN20100	ONL Black	ON 3		
ON	1NO-1NC	-	UWQN21100	ON: Black OFF: Red	6 23 OFF 36		
OFF	2NO	-	UWQN22000		70 (2 blocks) 15.5		
⊕ ⊕ (€	2NC	-	UWQN20200				
Flush Twin Maintained	Тор	Bottom					
ABBN11	1NO	-	ABBN1110	Black (B), green (G), and red (R)	M3.5 Terminal Screw		
	1NC	-	ABBN1101	buttons are sup-			
	1NO-1NC	-	ABBN1111	unit.	930		
	2NO	-	ABBN1120	Other color buttons			
	2NC	-	ABBN1102	are separately ordered. See page 61.	57 Panel Thickness 0.8 to 7.5		
⊕ ⊕ (€	2NO-2NC		ABBN1122				
Mushroom Twin Maintained	Тор	Bottom					
(Without buttons) ABBN33	1NO	-	ABBN3310		M3.5 Terminal Screw 21		
	1NC	-	ABBN3301				
	1NO-1NC	-	ABBN3311	Order buttons separately.			
1	2NO	_	ABBN3320	See page 61.			
	2NC	-	ABBN3302		57 Panel Thickness 0.8 to 7.5		
⊕ ⊕ (€	2NO-2NC	-	ABBN3322				

- Round bezel (metal): Chrome-plated
- Other contact arrangements and gold-plated silver contacts are also available. See page 11.
- Square Twin (Momentary): Two independent momentary switches are contained in one unit, each operated by ON or OFF button. With the ø30 adapter removed form the sleeve, the unit can mount in a ø25.5mm mounting hole for the ø25 series.
- Square Twin (Maintained): The contact operates when ON button is pressed and is maintained in the depressed position. The button is reset by pressing the OFF button.
- Twin Maintained: The contact operates when the top button is pressed and is maintained in the depressed position. The button is reset by pressing the bottom button.

 Different combinations of flush, extended buttons, and colors are available (ABN1B-*, ABN2B-*). See page 61.

Mushroom buttons for the ABBN33 are ordered separately. Specify the color code (ABN3B-*). See page 61.

ø30 ø30 Series Pilot Lights

Dome Types

Shape	Lamp	Input Type	Lamp Receptacle	Type No.	② Lens/LED Color Code	Applicable Lamp
Dome APN1 APNE1	Without Lamp	/ithout Lamp Full Voltage	BA9S	APN199@	A: amber C: clear G: green O: orange	LSTD LS (1W)
			E12	APNE199@	R: red S: blue W: white Y: yellow	LETD LE (2W)
		Transformer	BA9S	APN13DN2	A: amber G: green	LSTD-62
			E12	APNE13DN2	PW: pure white**	LETD-62
	LED	DC-DC Converter*	BA9S	APN116DDN®	S: blue	LSTD-62
11/5			E12	APNE116DDN®	W: white Y: yellow	LETD-62
	Incandescent	descent Transformer	BA9S	APN132	C: clear G: green O: orange	LS-6 (1W)
⊕ ⊕ (€	meandescent	Hansionne	E12	APN132	R: red S: blue W: white	LE-8 (2W)

• Operating Voltage Code


Specify an operating voltage code in place of ③ in the Type No.

③ Operating Vo	③ Operating Voltage Code							
LED Transformer BA9S and E12 Types Incandescent Transformer BA9S Type	Incandescent Transformer E12 Type							
16: 100/110V AC	18: 100/110V AC							
116: 115V AC	118: 115V AC							
126: 120V AC	128: 120V AC							
26: 200/220V AC	28: 200/220V AC							
236: 230V AC	238: 230V AC							
246: 240V AC	248: 240V AC							
386: 380V AC	388: 380V AC							
46: 400/440V AC	48: 400/440V AC							
486: 480V AC (incandescent only)	488: 480V AC							


- Specify a lens/LED color code in place of ② in the Type No. Use the white lens (W) for LED pure white illumination.
- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer and DC-DC converter types contain an LED lamp: LSTD-6@ or LETD-6@ (rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC) or LE-8 (2W, 18V AC/DC).
- * DC-DC converter types are not approved by UL and CSA, and not CE compliant (operating voltage 90 to 140V DC).
- ** Pure white is available for BA9S lamp base types only.

Dimensions

• Full Voltage Type



- Transformer Type
- DC-DC Converter Type



Square / Rectangular (Marking) Types

Shape	Lamp	Input Type	Lamp Receptacle	Type No.	② Lens/LED Color Code	Applicable Lamp
Square UPQN3B	Without Lamp	Full Voltage	BA9S	UPQN3B99@	A: amber C: clear G: green O: orange R: red S: blue W: white Y: yellow	LSTD LS (1W)
	LED	Transformer	BA9S	UPQN3B3D2	A: amber G: green R: red	LSTD-62
	LED	DC-DC Converter*	BA9S	UPQN3B16DD@	S: blue W: white Y: yellow	LSTD-62
⊕ ⊕ (€	Incandescent	Transformer	BA9S	UPQN3B@@	C: clear G: green O: orange R: red S: blue W: white	LS-6 (1W)
Rectangular (Marking Type) UPQN4	Without Lamp	Full Voltage	BA9S	UPQN499@	A: amber G: green O: orange R: red S: blue W: white Y: yellow	LSTD LS (1W)
	LED	Transformer	BA9S	UPQN43D2	A: amber G: green R: red S: blue W: white Y: yellow	LSTD-62
		DC-DC Converter*	BA9S	UPQN416DD@		LSTD-62
⊕ 6 €	Incandescent	Transformer	BA9S	UPQN432	G: green O: orange R: red S: blue W: white	LS-6 (1W)
Rectangular (Marking Type) UPQNE4 UPQN4	Without Lamp	Full Voltage	E12	UPQNE499@	A: amber G: green O: orange R: red S: blue W: white Y: yellow	LETD LE (2W)
	LED	Transformer	E12	UPQNE43D2	A: amber G: green R: red	LETD-62
		DC-DC Converter*	E12	UPQNE416DD@	S: blue W: white Y: yellow	LETD-62
(f) (g) (€	Incandescent	Transformer	E12	UPQN43@	G: green O: orange R: red S: blue W: white	LE-8 (2W)

ø30 ø30 Series Pilot Lights

Operating Voltage Code


Specify an operating voltage code in place of 3 in the Type No.

		<u> </u>						
	③ Operating Voltage Code							
	nsformer BA9S and E12 Types scent Transformer BA9S Type	Incandescent Transformer E12 Ty						
16:	100/110V AC	18: 100/110V AC						
116:	115V AC	118: 115V AC						
126:	120V AC	128: 120V AC						
26:	200/220V AC	28: 200/220V AC						
236:	230V AC	238: 230V AC						
246:	240V AC	248: 240V AC						
386:	380V AC	388: 380V AC						
46:	400/440V AC	48: 400/440V AC						
486:	480V AC (incandescent only)	488: 480V AC						


- Specify a lens/LED color code in place of @ in the Type No.
- On the rectangular marking type, a clear lens and a color marking plate are used for white illumination.
- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer and DC-DC converter types contain an LED lamp: LSTD-6@ or LETD-6@ (rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC) or LE-8 (2W, 18V AC/DC).
- Marking plate for the rectangular marking type: 24 × 30 mm, 2 mm thick
- * DC-DC converter types are not approved by UL and CSA, and not CE compliant (operating voltage 90 to 140V DC).

Dimensions


• Square Full Voltage Type **UPQN3B**




• Rectangular Full Voltage Type **UPQN4**




• Rectangular Full Voltage Type **UPQNE4**




- Square Transformer Type
- Square DC-DC Converter Type UPQN3B



- Rectangular Transformer Type
- Rectangular DC-DC Converter Type UPQN4




- Rectangular Transformer Type
- Rectangular DC-DC Converter Type **UPQNE4**



All dimensions in mm.


Reflector

- 1. The lamp housing of the square type LED illuminated pilot lights has a built-in reflector.
- 2. Make sure that the reflector does not fall off when removing the lens or marking plate.
- 3. When replacing the LED lamp of UPQNE4 (rectangular) type, use a lamp holder tool (OR-55).
- 4. To remove the reflector, insert a flat screwdriver inside the groove of the reflector and lightly push out.



Panel Mounting

- 1. Tighten the square ring to the operator and position the ring correctly.
- 2. Lightly tighten the screw to secure the pilot light onto the panel.



Push-to-Check Types (1W) **Incandescent**


Shape	Lamp	Input Type	Lamp Receptacle	Type No.	② Lens/LED Color Code	Applicable Lamp
Push-to-Check APN1*P						
Without La	Without Lamp	np Full Voltage	BA9S	APN199P@	C: clear G: green O: orange	LS (1W)
	Incandescent	Transformer	BA9S	APN13P2	R: red S: blue W: white	LS-6 (1W)
(h) (sh) (€						

• Operating Voltage Code
Specify an operating voltage code in place of ③ in the Type No.

3	③ Operating Voltage Code					
16:	100/110V AC					
116:	115V AC					
126:	120V AC					
26:	200/220V AC					
236:	230V AC					
246:	240V AC					
386:	380V AC					
46:	400/440V AC					
486:	480V AC					

- Specify a lens color code in place of @ in the Type No.
- Full voltage types do not contain a lamp. Order incandescent lamps separately. For lamps, see page 63.
- Transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC).


Circuit Example



Note: The lamp of push-to-check pilot light is not connected to the contact terminal. To connect, refer to the diagram on the left.

Dimensions

• Push-to-Check APN1*P



Round Extended Illuminated Pushbuttons LED

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALN29911DN2	
ALN2			Without Lamp	Full Voltage	2NO	ALN29920DN2	LSTD
AOLN2 ALNE2		Mamantani			2NC	ALN29902DN2	
AOLNE2		Momentary			1NO-1NC	ALN2311DN2	
			LED	Transformer	2NO	ALN2320DN2	LSTD-62
	BA9S				2NC	ALN2302DN2	
	DA95				1NO-1NC	AOLN29911DN2	
			Without Lamp	Full Voltage	2NO	AOLN29920DN2	LSTD
		Maintained			2NC	AOLN29902DN2	
		Maintained	LED	Transformer	1NO-1NC	AOLN2311DN2	LSTD-6@
La non					2NO	AOLN2320DN2	
I Can					2NC	AOLN2302DN2	
			Without Lamp	Full Voltage	1NO-1NC	ALNE29911DN®	LETD
		Momentary			2NO	ALNE29920DN®	
					2NC	ALNE29902DN®	
		Momentary		Transformer	1NO-1NC	ALNE2311DN2	LETD-62
			LED		2NO	ALNE2@20DN@	
	E12				2NC	ALNE2302DN2	
	E12				1NO-1NC	AOLNE29911DN2	
			Without Lamp	Full Voltage	2NO	AOLNE29920DN2	LETD
		Maintained			2NC	AOLNE29902DN2	
		iviaii itaii ieu			1NO-1NC	AOLNE2311DN2	LETD-62
			LED	Transformer	2NO	AOLNE2@20DN@	
					2NC	AOLNE2302DN2	


Color Code and Operating Voltage Code

② Lens/LED Color Code	③ Operating Voltage Code					
LED Illuminated Type	LED Transformer BA9S and E12 Types					
Specify a lens/LED color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No					
A: amber G: green PW: pure white (BA9S type only) R: red S: blue W: white Y: yellow	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC					
Use the white lens (W) for LED pure white illumination.	46: 400/440V AC					


- Full voltage types do not contain a lamp. Order LED lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp: LSTD-6@ or LETD-6@ (rated voltage 6V AC/DC).

Dimensions


• ALN2/AOLN2 BA9S/Full Voltage




• ALNE2/AOLNE2 E12/Full Voltage



• ALN2/AOLN2 BA9S/Transformer



• ALNE2/AOLNE2 E12/Transformer



Round Extended Illuminated Pushbuttons Incandescent


Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALN9911@	
ALN			Without Lamp	Full Voltage	2NO	ALN99202	LS (1W)
ALNE		Momentary			2NC	ALN9902@	
		Momentary			1NO-1NC	ALN3112	
			Incandescent	Transformer	2NO	ALN3202	LS-6
	BA9S				2NC	ALN3022	
TE TO	DA95				1NO-1NC	AOLN99112	
TE CO			Without Lamp	Full Voltage	2NO	AOLN99202	LS (1W)
		Maintained			2NC	AOLN9902@	1
-		Maintained	Incandescent	Transformer	1NO-1NC	AOLN3112	LS-6
					2NO	AOLN3202	
(I)					2NC	AOLN3022	
			Without Lamp	Full Voltage	1NO-1NC	ALNE9911@	LE (2W)
AOLN AOLNE					2NO	ALNE9920@	
/ OLIVE		NA to			2NC	ALNE99022	
		Momentary		Transformer	1NO-1NC	ALN3112	LE-8
			Incandescent		2NO	ALN3202	
	E12				2NC	ALN3022	
	E 12				1NO-1NC	AOLNE99112	
160			Without Lamp	Full Voltage	2NO	AOLNE99202	LE (2W)
		B.A. data take a sal			2NC	AOLNE99022	
		Maintained			1NO-1NC	AOLN3112	
			Incandescent	Transformer	2NO	AOLN3202	LE-8
					2NC	AOLN3022	

Color Code and Operating Voltage Code

② Lens Color Code	3 Operating Voltage Code					
Incandescent Illuminated Type	andescent Illuminated Type Incandescent Transformer BA9S Type Incandescent Tra					
Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place	e of ③ in the Type No.				
C: clear G: green O: orange R: red S: blue W: white	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC	18: 100/110V AC 118: 115V AC 128: 120V AC 28: 200/220V AC 238: 230V AC 248: 240V AC 388: 380V AC 48: 400/440V AC 488: 480V AC				

- Full voltage types do not contain a lamp. Order incandescent lamps separately. For lamps, see page 63.
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC) or LE-8 (2W, 18V AC/DC).

Dimensions



Round Extended with Half Shroud Illuminated Pushbuttons LED

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALGN29911DN2	
ALGN2			Without Lamp	Full Voltage	2NO	ALGN29920DN2	LSTD
AOLGN2 ALGNE2		Mamantani			2NC	ALGN29902DN2	
AOLGNE2		Momentary			1NO-1NC	ALGN2311DN2	
			LED	Transformer	2NO	ALGN2320DN2	LSTD-62
	BA9S				2NC	ALGN2302DN2	
	DA95				1NO-1NC	AOLGN29911DN2	
			Without Lamp	Full Voltage	2NO	AOLGN29920DN©	LSTD
		Maintained			2NC	AOLGN29902DN2	
		Maintained	LED	Transformer	1NO-1NC	AOLGN2311DN2	LSTD-62
The same					2NO	AOLGN2@20DN@	
					2NC	AOLGN2@02DN@	
			Without Lamp	Full Voltage	1NO-1NC	ALGNE29911DN2	LETD
					2NO	ALGNE29920DN2	
		N4			2NC	ALGNE29902DN2	
		Momentary	LED		1NO-1NC	ALGNE2311DN2	LETD-62
				Transformer	2NO	ALGNE2320DN2	
	E12				2NC	ALGNE2302DN2	
	E12				1NO-1NC	AOLGNE29911DN©	
			Without Lamp	Full Voltage	2NO	AOLGNE29920DN ²	LETD
		Maintained			2NC	AOLGNE29902DN2	1
		iviaii itaii ieu			1NO-1NC	AOLGNE2311DN2	LETD-62
m @ ((LED	Transformer	2NO	AOLGNE2@20DN@	
					2NC	AOLGNE2@02DN@	


• Color Code and Operating Voltage Code

② Lens/LED Color Code	③ Operating Voltage Code
LED Illuminated Type	LED Transformer BA9S and E12 Types
Specify a lens/LED color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.
A: amber G: green PW: pure white (BA9S type only) R: red S: blue W: white Y: yellow Use the white lens (W) for LED pure white illumination.	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC


- Full voltage types do not contain a lamp. Order LED lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp: LSTD-6@ or LETD-6@ (rated voltage 6V AC/DC).

Dimensions


• ALGN2/AOLGN2 BA9S/Full Voltage




• ALGNE2/AOLGNE2 E12/Full Voltage



• ALGN2/AOLGN2 BA9S/Transformer



• ALGNE2/AOLGNE2 E12/Transformer





Round Extended with Half Shroud Illuminated Pushbuttons Incandescent

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALN9G911@	
ALN*G			Without Lamp	Full Voltage	2NO	ALN9G920@	LS (1W)
ALNE*G	BA9S	Momentary			2NC	ALN9G902@	
В	DASS	Momentary	Incandescent	Transformer	1NO-1NC	ALN3112	LS-6
					2NO	ALN3202	
					2NC	ALN3022	
1	F40		Without Lamp	Full Voltage	1NO-1NC	ALNE9G9112	LE (2W)
					2NO	ALNE9G9202	
E12		Momentary			2NC	ALNE9G9022	
	E 12	Momentary			1NO-1NC	ALN3112	LE-8
₩ 6 (€	6.66		Incandescent	Transformer	2NO	ALN3202	
					2NC	ALN3022	


Color Code and Operating Voltage Code

② Lens Color Code	③ Operating Voltage Code				
Incandescent Illuminated Type	Incandescent Transformer BA9S Type	Incandescent Transformer E12 Type			
Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place	e of ③ in the Type No.			
C: clear G: green O: orange R: red S: blue W: white	1G6: 100/110V AC 11G6: 115V AC 12G6: 120V AC 2G6: 200/220V AC 23G6: 230V AC 24G6: 240V AC 38G6: 380V AC 4G6: 400/440V AC 48G6: 480V AC	1G8: 100/110V AC 11G8: 115V AC 12G8: 120V AC 2G8: 200/220V AC 23G8: 230V AC 24G8: 240V AC 38G8: 380V AC 4G8: 400/440V AC 48G8: 480V AC			


- Full voltage types do not contain a lamp. Order incandescent lamps separately. For lamps, see page 63.
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC) or LE-8 (2W, 18V AC/DC).

Dimensions


ALN*G Momentary BA9S/Full Voltage




ALNE*G Momentary E16/Full Voltage



ALN*G Momentary BA9S/Transformer



ALNE*G Momentary E16/Transformer



Round Extended with Full Shroud Illuminated Pushbuttons LED

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALFN29911DN®	
ALFN2			Without Lamp	Full Voltage	2NO	ALFN29920DN®	LSTD
AOLFN2 ALFNE2		Momentary			2NC	ALFN29902DN®	
AOLFNE2		Momentary			1NO-1NC	ALFN2311DN2	
			LED	Transformer	2NO	ALFN2320DN2	LSTD-6@
	BA9S				2NC	ALFN2302DN2	
	DA95				1NO-1NC	AOLFN29911DN2	
			Without Lamp	Full Voltage	2NO	AOLFN29920DN2	LSTD
		Maintained			2NC	AOLFN29902DN2	
		Maintained	LED	Transformer	1NO-1NC	AOLFN2311DN2	LSTD-62
74 600					2NO	AOLFN2320DN2	
					2NC	AOLFN2302DN2	
		Momentary	Without Lamp	Full Voltage	1NO-1NC	ALFNE29911DN2	LETD
8					2NO	ALFNE29920DN2	
					2NC	ALFNE29902DN2	
			LED	Transformer	1NO-1NC	ALFNE2311DN2	LETD-62
					2NO	ALFNE2320DN2	
	E12				2NC	ALFNE2302DN2	
	E12				1NO-1NC	AOLFNE29911DN2	
			Without Lamp	Full Voltage	2NO	AOLFNE29920DN2	LETD
		Maintainad			2NC	AOLFNE29902DN2	
		Maintained			1NO-1NC	AOLFNE2311DN2	
			LED	Transformer	2NO	AOLFNE2320DN2	LETD-62
(I)					2NC	AOLFNE2302DN2	


• Color Code and Operating Voltage Code

② Lens/LED Color Code	③ Operating Voltage Code
LED Illuminated Type	LED Transformer BA9S and E12 Types
Specify a lens/LED color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.
A: amber G: green PW: pure white (BA9S type only) R: red S: blue W: white Y: yellow Use the white lens (W) for LED pure white illumination.	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC


- Full voltage types do not contain a lamp. Order LED lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp: LSTD-6@ or LETD-6@ (rated voltage 6V AC/DC).

Dimensions


ALFN2/AOLFN2 BA9S/Full Voltage




• ALFNE2/AOLFNE2 E12/Full Voltage



• ALFN2/AOLFN2 **BA9S/Transformer**



• ALFNE2/AOLFNE2 E12/Transformer





Round Extended with Full Shroud Illuminated Pushbuttons Incandescent


Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALN9F9112	
ALN*F			Without Lamp	Full Voltage	2NO	ALN9F920@	LS (1W)
ALNE*F		Managantani			2NC	ALN9F9022	
		Momentary			1NO-1NC	ALN3112	
			Incandescent	Transformer	2NO	ALN3202	LS-6
	DAGG				2NC	ALN3022	
	BA9S				1NO-1NC	AOLN9F911@	
The state of the s			Without Lamp	Full Voltage	2NO	AOLN9F9202	LS (1W)
		Maintained			2NC	AOLN9F902@	1
		Maintained	Incandescent	Transformer	1NO-1NC	AOLN3112	LS-6
					2NO	AOLN3202	
⊕ ⊕ (€					2NC	AOLN3022	
AOLNIE			Without Lamp	Full Voltage	1NO-1NC	ALNE9F911@	LE (2W)
AOLN*F AOLNE*F					2NO	ALNE9F920@	
A CENTER I		Managantani			2NC	ALNE9F902@	
		Momentary		Transformer	1NO-1NC	ALN3112	LE-8
			Incandescent		2NO	ALN3202	
	E12				2NC	ALN3022	
	E1Z				1NO-1NC	AOLNE9F911@	
			Without Lamp	Full Voltage	2NO	AOLNE9F920@	LE (2W)
- 6		NA - i - i - i I			2NC	AOLNE9F902@	1
		Maintained			1NO-1NC	AOLN3112	
			Incandescent	Transformer	2NO	AOLN3202	LE-8
UL STED SP (€					2NC	AOLN3022	

Color Code and Onerethan Valtage Code

② Lens Color Code	3 Operating Voltage Code						
Incandescent Illuminated Type	Incandescent Transformer BA9S Type Incandescent Transformer E						
Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place	e of ③ in the Type No.					
C: clear G: green O: orange R: red S: blue W: white	1F6: 100/110V AC 11F6: 115V AC 12F6: 120V AC 2F6: 200/220V AC 23F6: 230V AC 24F6: 240V AC 38F6: 380V AC 4F6: 400/440V AC 48F6: 480V AC	1F8: 100/110V AC 11F8: 115V AC 12F8: 120V AC 2F8: 200/220V AC 23F8: 230V AC 24F8: 240V AC 38F8: 380V AC 4F8: 400/440V AC 48F8: 480V AC					

- Full voltage types do not contain a lamp. Order incandescent lamps separately. For lamps, see page 63.
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC) or LE-8 (2W, 18V AC/DC).

Dimensions



ø30 ø30 Series Illuminated Pushbuttons

Mushroom (ø40) Illuminated Pushbuttons **LED**

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
ø40 Mushroom					1NO-1NC	ALN39911DN2	
ALN3			Without Lamp	Full Voltage	2NO	ALN39920DN2	LSTD
AOLN3 ALNE3		Momentary			2NC	ALN39902DN2	
AOLNE3		Momentary			1NO-1NC	ALN3@11DN@	
			LED	Transformer	2NO	ALN3320DN2	LSTD-62
	BA9S				2NC	ALN3@02DN@	
	DA93				1NO-1NC	AOLN39911DN2	
			Without Lamp	Full Voltage	2NO	AOLN39920DN2	LSTD
		Maintained			2NC	AOLN39902DN2	
		Maintained	LED	Transformer	1NO-1NC	AOLN3@11DN@	LSTD-62
					2NO	AOLN3@20DN@	
					2NC	AOLN3@02DN@	
			Without Lamp	Full Voltage	1NO-1NC	ALNE39911DN2	LETD
					2NO	ALNE39920DN ²	
		Momentary			2NC	ALNE39902DN2	
		Momentary			1NO-1NC	ALNE3311DN2	LETD-62
17 5			LED	Transformer	2NO	ALNE3@20DN@	
	E12				2NC	ALNE3@02DN@	
	L12				1NO-1NC	AOLNE39911DN2	
			Without Lamp	Full Voltage	2NO	AOLNE39920DN2	LETD
		Maintained			2NC	AOLNE39902DN2	1
		ivialitalited			1NO-1NC	AOLNE3@11DN@	LETD-62
⊕ ⊕ (€			LED	Transformer	2NO	AOLNE3@20DN@	
U _{LISTED} ∰ (€					2NC	AOLNE3@02DN@	


• Color Code and Operating Voltage Code

② Lens/LED Color Code	③ Operating Voltage Code			
LED Illuminated Type	LED Transformer BA9S and E12 Types			
Specify a lens/LED color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.			
A: amber G: green R: red S: blue W: white Y: yellow	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC			


- Full voltage types do not contain a lamp. Order LED lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp: LSTD-62 or LETD-62 (rated voltage 6V AC/DC).

Dimensions


ALN3/AOLN3 BA9S/Full Voltage




ALNE3/AOLNE3 E12/Full Voltage



• ALN3/AOLN3 BA9S/Transformer



ALNE3/AOLNE3 E12/Transformer





Square and Rectangular Extended Illuminated Pushbuttons Incandescent


Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Square Extended					1NO-1NC	ULQN99112	
ULQN			Without Lamp	Full Voltage	2NO	ULQN9920@	LS (1W)
		Momentary			2NC	ULQN9902@	
18		Momentary			1NO-1NC	ULQN3112	
18			Incandescent	Transformer	2NO	ULQN3202	LS-6
Un Off (BA9S				2NC	ULQN3022	
UOLQN	DA93				1NO-1NC	UOLQN9911@	
			Without Lamp	Full Voltage	2NO	UOLQN9920@	LS (1W)
140		Maintained			2NC	UOLQN9902@	
			Incandescent	Transformer	1NO-1NC	UOLQN3112	LS-6
					2NO	UOLQN3202	
Unsted & CE					2NC	UOLQN3022	
Rectangular (Marking Type)			Without Lamp	Full Voltage	1NO-1NC	ULQN9B9112	LS (1W)
ULQN*B		Managara			2NO	ULQN9B9202	
					2NC	ULQN9B9022	
		Momentary			1NO-1NC	ULQN3112	LS-6
			Incandescent	Transformer	2NO	ULQN3202	
(I)	BA9S				2NC	ULQN3022	
UOLQN*B	DA93				1NO-1NC	UOLQN9B911@	
			Without Lamp	Full Voltage	2NO	UOLQN9B9202	LS (1W)
1		Maintained			2NC	UOLQN9B9022	
		ivialitaliteu			1NO-1NC	UOLQN3112	LS-6
			Incandescent	Transformer	2NO	UOLQN3202	
ULISTED & C E					2NC	UOLQN3022	

Color Code and Operating Voltage Code

② Lens Color Code	③ Operating Voltage Code					
Incandescent Illuminated Type	Incandescent Transformer Square Extended Type	Incandescent Transformer Rectangular Marking Type				
Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place	ce of ③ in the Type No.				
C: clear (square type only) G: green O: orange R: red S: blue W: white Clear lens is not available for the rectangular type.	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC	1B6: 100/110V AC 11B6: 115V AC 12B6: 120V AC 2B6: 200/220V AC 23B6: 230V AC 24B6: 240V AC 38B6: 380V AC 4B6: 400/440V AC 48B6: 480V AC				

- Full voltage types do not contain a lamp. Order incandescent lamps separately. For lamps, see page 63.
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC).

Dimensions



ø30 ø30 Series Illuminated Pushbuttons

Incandescent Push Turn Lock Switches

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
ALN*L					1NO-1NC	ALN9L911@	
	BA9S	Push Turn Lock	Without Lamp	Full Voltage	2NO	ALN9L920@	LS (1W)
TE CO					2NC	ALN9L9022	
			Incandescent	Transformer	1NO-1NC	ALN3112	
					2NO	ALN3202	LS-6
(l) (step (€					2NC	ALN3022	


• Color Code and Operating Voltage Code

② Lens Color Code	③ Operating Voltage Code				
Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.				
G: green O: orange R: red S: blue W: white	1L6: 100/110V AC 11L6: 115V AC 12L6: 120V AC 2L6: 200/220V AC 23L6: 230V AC 24L6: 240V AC 38L6: 380V AC 4L6: 400/440V AC 48L6: 480V AC				


- Full voltage types do not contain a lamp. Order incandescent lamps separately. For lamps, see page 63.
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC).
- Push Turn Lock: Knob is maintained when turned clockwise in the depressed position and is reset when turned counterclockwise.

Dimensions

• ALN*L BA9S/Full Voltage



• ALN*L BA9S/Transformer



Pushlock Turn Reset / Push Turn Lock Types **LED**

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp	
ø40 Mushroom					1NO-1NC	AVLN39911DNR		
Pushlock Turn Reset			Without Lamp	Full Voltage	2NO	AVLN39920DNR	LSTD	
AVLN3 AVLNE3	BA9S	Pushlock			2NC	AVLN39902DNR		
7.02.020	BASS	Turn Reset			1NO-1NC	AVLN3311DNR		
			LED	Transformer	2NO	AVLN3@20DNR	LSTD-62	
					2NC	AVLN3@02DNR		
					1NO-1NC	AVLNE39911DNR		
Ta		Pushlock Turn Reset	Without Lamp	Full Voltage	2NO	AVLNE39920DNR	LETD	
	E12				2NC	AVLNE39902DNR		
			LED	Transformer	1NO-1NC	AVLNE3@11DNR	LETD-62	
(h) 6					2NO	AVLNE3@20DNR		
USTED SP.					2NC	AVLNE3@02DNR		
ø40 Mushroom Push Turn Lock			Without Lamp	Full Voltage	1NO-1NC	AJLN39911DN@		
AJLN3					2NO	AJLN39920DN©	LSTD	
	BA9S	Push Turn			2NC	AJLN39902DN@		
Lac ₄	DAGO	Lock			1NO-1NC	AJLN3311DN2		
			LED	Transformer	2NO	AJLN3@20DN@	LSTD-62	
(l) (g) (€					2NC	AJLN3@02DN@		

Color Code and Operating Voltage Code


② Lens/LED Color Code	③ Operating Voltage Code						
LED Illuminated Type	LED Transformer BA9S Types						
Specify a lens/LED color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.						
A: amber G: green R: red W: white Y: yellow	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC						

- Full voltage types do not contain a lamp. Order LED lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp: LSTD-6@ or LETD-6@ (rated voltage 6V AC/DC).
- Pushlock Turn Reset: Lens is maintained when pressed and is reset when turned clockwise. Red lens only.

Note: AVNL3 and AVNLE3 pushlock turn reset switches cannot be used as emergency stop switches. When emergency stop switches are required, use the HN1E series emergency stop switches (ISO 13850 and IEC 60947-5-5 compliant).

• Push Turn Lock: Lens is maintained when turned clockwise in the depressed position and is reset when turned counterclockwise.

Dimensions



Pushlock Turn Reset / Push Turn Lock Types Incandescent

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
ø40 Mushroom					1NO-1NC	AVLN39911NR	
Pushlock Turn Reset			Without Lamp	Full Voltage	2NO	AVLN39920NR	LS (1W)
AVLN3 AVLNE3	BA9S	Pushlock			2NC	AVLN39902NR	
/ WEINEO	DASS	Turn Reset			1NO-1NC	AVLN3@11NR	
			Incandescent	Transformer	2NO	AVLN3@20NR	LS-6
					2NC	AVLN3@02NR	
					1NO-1NC	AVLNE39911NR	
		Pushlock Turn Reset	Without Lamp	Full Voltage	2NO	AVLNE39920NR	LE (2W)
	E12				2NC	AVLNE39902NR	
			Incandescent	Transformer	1NO-1NC	AVLNE3@11NR	LE-8
(h) (A					2NO	AVLNE3@20NR	
UNITED (S)					2NC	AVLNE3@02NR	
ø40 Mushroom Push Turn Lock			Without Lamp	Full Voltage	1NO-1NC	AJLN39911N2	
AJLN3					2NO	AJLN39920N@	LS (1W)
	BA9S	Push Turn			2NC	AJLN39902N2	
in the state of th	DAGO	Lock			1NO-1NC	AJLN3311N2	
			Incandescent	Transformer	2NO	AJLN3320N2	LS-6
Usited GF (E					2NC	AJLN3302N2	

• Color Code and Operating Voltage Code


② Lens Color Code	③ Operating Voltage Code					
Incandescent Illuminated Type	Incandescent Transformer BA9S Type	Incandescent Transformer E12 Type				
Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place	of ③ in the Type No.				
G: green O: orange R: red	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC	18: 100/110V AC 118: 115V AC 128: 120V AC 28: 200/220V AC 238: 230V AC 248: 240V AC 388: 380V AC				
	46: 400/440V AC 486: 480V AC	48: 400/440V AC 488: 480V AC				

- Full voltage types do not contain a lamp. Order incandescent lamps separately. For lamps, see page 63.
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC) or LE-8 (2W, 18V AC/DC).
- Pushlock Turn Reset: Lens is maintained when pressed and is reset when turned clockwise. Red lens only.

Note: AVNL3 and AVNLE3 pushlock turn reset switches cannot be used as emergency stop switches. When emergency stop switches are required, use the HN1E series emergency stop switches (ISO 13850 and IEC 60947-5-5 compliant).

• Push Turn Lock: Lens is maintained when turned clockwise in the depressed position and is reset when turned counterclockwise.

Dimensions



ASN Selector Switches (Knob Operator Type)

No. of Positions	Shape Co	ntact Arra	angem	ent Cl	nart		Knob: Black Round bezel (metal): Chrome-plated Units marked with ★ differ in shape. See page 36 for dimensions. Nameplates are ordered separately.				
	Contact	Contact Block Opera			Operator Position		Maintained	Spring Return from Right	Maintained	Spring Return from Left	
	Code (ASN)	Mounting Position	Туре	L	R		LR	LR	L	LR	
	10 (1NO)	1 2	NO Dummy		•		ASN310	ASN410			
	11 (1NO-1NC)	1 2	NO NC	•	•		ASN311	ASN411			
	20 (2NO)	1 2	NO NO		•		ASN320	ASN420			
2-position	22 (2NO-2NC)	1 2 3 4	NO NC NO NC	•	•		ASN322	ASN422	_	_	
90° 2	7S (1NO-1NC)	1 2	NO NC				ASN37S	ASN47S			
0	10 (1NO)	1 2	NO Dummy	•					ASN3010	ASN4010	
	11 (1NO-1NC)	1	NO	•				_	ASN3011	ASN4011	
	20	2 1	NC NO	•	•				ASN3020	ASN4020	
	(2NO) 22	2 1 2	NO NO NC	•	•		_				
	(2NO-2NC)	3	NO NC	•	•				ASN3022	ASN4022	
	7S (1NO-1NC)	1 2	NO NC				•		ASN307S	ASN407S	
	Contact Code (ASN)	Contact		Opera	ator Pos	sition	Maintained	Spring Return from Left	Maintained	Spring Return from Right	
		Mounting Position	Туре	L	С	R	L C R	L C R	L C R	L C R	
	11 (1NO-1NC)	1 2	NO NC	•		•	ASN111	ASN211			
	22 (2NO-2NC)	1 2 3 4	NO NC NO NC	•		•	ASN122	ASN222			
	5S (2NO-2NC)	1 2 3 4	NO NO NC NC	•		•	ASN15S ★	ASN25S ★	_	_	
tion	7S (2NC)	2	NC NC				ASN17S ★	ASN27S ★			
45° 3-position	8S (4NC)	1 2 3 4	NC NC NC				ASN18S ★	ASN28S ★			
4	11 (1NO-1NC)	1 2	NO NC	•		•			ASN1011	ASN2011	
	22 (2NO-2NC)	1 2 3 4	NO NC NO	•		•			ASN1022	ASN2022	
	5S (2NO-2NC)	1 2 3 4	NO NC NO	•		•	_	_	ASN105S ★	ASN205S ★	
	7S (2NC)	1 2	NC NC						ASN107S ★	ASN207S ★	
	8S (4NC)	1 2 3 4	NC NC NC			-			ASN108S ★	ASN208S ★	

ASN Selector Switches (Lever Operator Type)

No. of Positions	Shape						ASN*L • Lever: Black • Round bezel (metal): Chrome-plated • Units marked with ★ differ in shape. See page 36 for dimensions. • Nameplates are ordered separately.				
8	Contact Arrangement Chart					oition	Waintained Maintained	Spring Return	Maintained	Spring Return	
	Contact Code (ASN)	Contact Block		Operator Position		SILION	Maintained	from Right	iviairitairied	from Left	
		Mounting Position	Туре	L	R		LR	L R	L R	L R	
	10 (1NO)	2	NO Dummy		•		ASN3L10	ASN4L10			
90° 2-position	11 (1NO-1NC)	1 2	NO NC	•	•		ASN3L11	ASN4L11		_	
	20 (2NO)	2	NO NO		•		ASN3L20	ASN4L20	_		
	22 (2NO-2NC) 7S (1NO-1NC)	1 2	NO NC	•	•		ASN3L22 ASN3L7S	ASN4L22			
		3 4	NO NC	•	•						
		1 2	NO NC	•				ASN4L7S			
	10 (1NO)	1 2	NO Dummy	•					ASN30L10	ASN40L10	
	11 (1NO-1NC)	1	NO	•				_	ASN30L11	ASN40L11	
	20	1	NC NO	•	•				ASN30L20	ASN40L20	
	(2NO) 22 (2NO-2NC) 7S	2 1	NO NO	•			_		ASN30L22	ASN40L22	
		3	NC NO	•	•		_				
		1	NC NO		•				ASN30L7S	ASN40L7S	
	(1NO-1NC)	2	NC			<u></u>		Spring Return		Spring Return	
	Contact Code (ASN)	Contact	Operator Position			Maintained	from Left	Maintained	from Right		
		Mounting Position	Туре	L	С	R	LR	L_ R	L R	L R	
	11 (1NO-1NC)	1 2	NO NC	•		•	ASN1L11	ASN2L11			
	22 (2NO-2NC)	1 2	NO NC	•		•	ASN1L22	A CNIOL OO			
		3	NO NC	•		•	ASNILZZ	ASN2L22	_	_	
	5S (2NO-2NC)	1 2	NO NO	•		•		ASN2L5S ★			
		3	NC NC				ASN1L5S ★				
luo	7S (2NC)	1 2	NC NC				ASN1L7S ★	ASN2L7S ★			
3-position	8S (4NC)	1 2	NC NC					ASN2L8S ★			
3-6.3		3	NC				ASN1L8S ★				
45°	11	1	NC NO			•			ASN10L11	ASN20L11	
	(1NO-1NC) 22 (2NO-2NC)	1	NC NO	•		•					
		3	NC NO	•		•			ASN10L22	ASN20L22	
	5S (2NO-2NC)	1	NC NO	•		•					
		3	NC NO	•			_	_	ASN10L5S ★	ASN20L5S ★	
		4	NC NC						101140170	400100170	
	(2NC)	2	NC NC						ASN10L7S ★	ASN20L7S ★	
	8S (4NC)	2	NC NC						ASN10L8S ★	ASN20L8S ★	
	. ,	4	NC								


ASN Key Selector Switches

	Shape						ASN*K • Cylinder: Chrome-plated				
S.							Round bezel (metal): Chrome-plated				
No. of Positions							On the spring-returned types, the keys can be released				
Sit							only from the maintained position. On the maintained types, the key can be released from every position. Key retained positions are also available. See page 12. • Key selector switch is supplied with two standard keys.				
<u>۾</u>											
9											
2	Contact Arrangement Chart						Two different keys are available upon request.				
							• Nameplates are ordered separa				
	_ Contact Block			Operator Position			Maintained	Spring Return from Right	Maintained	Spring Return from Left	
ion	Contact Code			-				from Right		from Left	
	(ASN)	Mounting Position	Туре	L	R		LR	L R	LR	L R	
	10 (1NO)	1 2	NO Dummy		•		ASN3K10	ASN4K10		_	
	11 (1NO-1NC) 20 (2NO)	2	NO NC	•	•	_	ASN3K11 ASN3K20	ASN4K11 ASN4K20	_		
		1	NO		•						
		1	NO NO		•						
	22	2	NC	•		-	ASN3K22	ASN4K22			
iso	(2NO-2NC)	3	NO		•		AGNONZZ				
90° 2-position		1	NC NO	•			A ON 101770				
	$(1\overline{NO}-1\overline{NC})$	2	NC				ASN3K7S	ASN4K7S			
	10 (1NO)	2	NO Dummy	•					ASN30K10	ASN40K10	
	11	1	NO	•					A CN1201/44	A CNIAOKAA	
	(1NO-1NC)	2	NC		•				ASN30K11	ASN40K11	
	20 (2NO)	2	NO NO	•		-			ASN30K20	ASN40K20	
	(2.10)	1	NO	•			_	_			
	22	2	NC		•				ASN30K22	ASN40K22	
	(2NO-2NC)	3	NO NC	•	•						
	_7S	1	NO						ASN30K7S	ASN40K7S	
	(1NO-1NC)	2	NC					Spring Return		Spring Return	
	Contact Code (ASN)	Contact	Operator Position			Maintained	from Left	Maintained	from Right		
		Mounting Position	Туре	L	С	R	L R	L R	L R	L R	
	11 (1NO-1NC)	1 2	NO NC	•		•	ASN1K11	ASN2K11			
	(INO-INC)	1	NO	•				ASN2K22 ASN2K5S	_	_	
	22 (2NO-2NC)	2	NC			•	ASN1K22 ASN1K5S				
		3	NO NC	•		•					
		1	NO	•							
	5S (1NO-1NC) (1NO-1NC)	2	NC			•					
		3	NO NC								
3-position	7S (1NO-1NC)	1 2	NO NC				ASN1K7S	ASN2K7S			
	(TNO-TNC)	1	NO						-		
%	8S (2NO-2NC)	2	NC				ASN1K8S	ASN2K8S			
45° 3		3	NO NC								
4	11	1	NO			•			ASN10K11	ASN20K11	
	(1NO-1NC) 22 (2NO-2NC)	1	NC NO	•					7.614161411	TONZORTI	
		2	NC	•		•			ASN10K22	ASN20K22	
		3	NO			•					
	5S (1NO-1NC) (1NO-1NC)	1	NC NO	•		•					
		2	NC	•			_	_	ASN10K5S	ASN20K5S	
		3	NO				_				
		1	NO NO								
	(1NO-1NC)	2	NC						ASN10K7S	ASN20K7S	
	8S (2NO-2NC)	1 2	NO NC						ASN10K8S	ASN20K8S	
		3	NO								
1	(ZNO-ZNC)	4	NC								


ø30 ø30 Series Selector Switches

Dimensions


Knob Operator Type




• Lever Operator Type




• Key Selector Type



Dimensions of knob operator type marked with ★




Dimensions of lever operator type marked with \star



All dimensions in mm.

• Contact Block Mounting Position and Contact Arrangement Chart






ASTN Selector Switches (Knob Operator Type)

No. of Positions	Shape						• Knob operator: Black • Round bezel (metal): Chrome-plated				
No.	Co	ntact Arra	angem	ent Cl	hart		(I)				
	Contact	Contact	Block	Opera	ator Po	sition	Maintained	Spring Return from Right		_	
2-position	Code (ASTN)	Mounting Position	Туре	L	R		LR	L	_	_	
° 2-pc	11 (1NO-1NC)	1 2	NO NC	•	•		ASTN3211	ASTN4211			
°06		1	NO		•				_	_	
	22	2	NO	_	•		ASTN3222	ASTN4222			
	(2NO-2NC)	3	NC NC	•							
	Contact	Contact				sition	Maintained	Spring Return from Left	Spring Return from Right	Spring Return Two-way	
	Code (ASTN)	Code (ASTN) Mounting Position Type L C R		L C R	L C R	L C R	L C R				
		1	NO	•							
	22 (2NO-2NC)	2	NO			•	ASTN1122	ASTN2122	ASTN20122	ASTN5122	
		3	NC				, , , , , , , , , , , , , , , , , , , ,	7.01112122	7.011120122	7.01110122	
		4	NC			_					
	00	2	NO NO	•		•					
	22 (2NO-2NC)	3	NC		•	•	ASTN1222	ASTN2222	ASTN20222	ASTN5222	
	(2110 2110)	4	NC								
		1	NO	-							
l _	40	2	NO			•	ASTN1340				
Ę.	(4NC)	3	NO	•			A31111340	_	_	_	
3-position		4	NO			•					
ا د		1	NO	•							
45°	22 (2NO-2NC)	3	NC NC			_	ASTN1422	_	ASTN20422	_	
14	(ZINO-ZINO)	4	NO			-					
	20	1	NO				A O.T. 14 50 S		A OTNIOSES		
	(2NO)	2	NO	•			ASTN1520	_	ASTN20520	_	
	, ,	1	NO			•					
	40	2	NO	•			ASTN1540		ASTN20540		
	(4NO)	3	NO			•	ACTIVIO	_	AUTIVZUUTU		
		4	NO	•							
	11 (1NO-1NC)	1 2	NC NO		•	•	ASTN1611	_	_		
	(INO-TNC)	1	NC		•	•					
	22	2	NO		_	•	. 				
	(2NO-2NC)	3	NC		•	-	ASTN1622	_	_	-	
	-/	4	NO			•					
	11 (1NO-1NC)	1 2	NO NC	•			_	_	_	ASTN5111	


- 1. The operator of the 2-way spring return unit may slightly deviate from the center position.
- 2. Turn the operator to each position accurately.

Contact Block Mounting Position and **Contact Arrangement Chart**





• Dimensions




ASTN Selector Switches (Lever Operator Type)


No. of Positions	Shape						ASTN*L		ever operator: Black ound bezel (metal): Ch	rome-plated	
No.	Co	ntact Arra	angem	ent Cl	hart		U _L ∰ (€				
	Contact	Contact	Block	Opera	ator Po	sition	Maintained	Spring Return from Right		_	
2-position	Code (ASTN)	Mounting Position	Туре	L	R		LR	LR	_	_	
° 2-pc	11 (1NO-1NC)	1 2	NO NC	•	•		ASTN32L11	ASTN42L11			
°06	00	1 2	NO NO		•				_	_	
	22 (2NO-2NC)	3	NC	•	•	-	ASTN32L22	ASTN42L22			
	,	4	NC	•		-					
	Contact	Contact	Block	Opera	ator Po	sition	Maintained	Spring Return from Left	Spring Return from Right	Spring Return Two-way	
	(ASTN)	Code ASTN) Mounting Position Type L C R		L C R	L_C_R	L C R	L C R				
		1	NO	•							
	22 (2NO-2NC)	2	NO NC			•	ASTN11L22	ASTN21L22	ASTN201L22	ASTN51L22	
		3	NC		5		-				
		1	NO	-		•					
	22	2	NO			•	ASTN12L22	ASTN22L22	ASTN202L22	ASTN52L22	
	(2NO-2NC)	3	NC		•		7.01112222		/\OTIVEOZEEZ	- · · · ·	
		1	NC NO	-							
_	40	2	NO			•					
ξi	(4NC)	3	NO	•			ASTN13L40	_	_	_	
isc	` ′	4	NO			•					
3-position		1	NO	•			1				
45°	22 (2NO-2NC)	3	NC NC				ASTN14L22	_	ASTN204L22	_	
4	(2.10)	4	NO				1				
	20	1	NO			•	ASTN15L20	_	ASTN205L20	_	
	(2NO)	2	NO	•			AUTIVIOLZU	_	AUTINZUULZU		
	40	1	NO			•	_				
	40 (4NO)	3	NO NO	•		•	ASTN15L40	_	ASTN205L40	_	
	(4140)	4	NO	•			_				
	11	1	NC		•		A CTNI4GL 44				
	(1NO-1NC)	2	NO			•	ASTN16L11	_	_		
		1	NC		•						
	22	3	NO NC			•	ASTN16L22	_	_	_	
	(2NO-2NC)	4	NO		•	•	-				
	11	1	NO	•		_				A OTNICAL AA	
	(1NO-1NC)	2	NC				_	_	_	ASTN51L11	

- 1. The operator of the 2-way spring return unit may slightly deviate from the center position.
- 2. Turn the operator to each position accurately.


Contact Block Mounting Position and **Contact Arrangement Chart**



• Dimensions




ASTN Key Selector Switches




- 1. The operator of the 2-way spring return unit may slightly deviate from the center position.
- 2. Turn the operator to each position accurately.

• Contact Block Mounting Position and **Contact Arrangement Chart**





Dimensions



Illuminated Selector Switches

90° 2-position

Shape					ASLN (Base BA9S)						
Contact Arrangement Chart				ırt	⊕ ⊕ €						
Contact	Conta Block			rator ition	Lamp	Input Type	Maintained	Spring Return from Right	Spring Return from Left		
Code	Mounting Position	Туре	L	R			L R	L R	R		
	1	NO		•	Without Lamp	Full Voltage	ASLN29911N2	ASLN219911N2	ASLN229911N2 *		
11 (1NO-1NC)	2	NC	•		LED	Transformer	ASLN2311DN2	ASLN21311DN2	ASLN22311DN2 *		
					Incandescent	Transformer	ASLN2311N2	ASLN21311N2	ASLN22311N2 *		
	1	NO		•	Without Lamp	Full Voltage	ASLN29920N2	ASLN219920N2	ASLN229920N② *		
20 (2NO)	2	NO		•	LED	Transformer	ASLN2320DN2	ASLN21320DN2	ASLN22320DN2 *		
					Incandescent	Transformer	ASLN2320N2	ASLN21320N2	ASLN22320N2 *		
	1 2	NO NC	•	•	Without Lamp	Full Voltage	ASLN29922N@	ASLN219922N2	ASLN229922N② *		
22 (2NO-2NC)	3 NO •		•		LED	Transformer	ASLN2322DN2	ASLN21322DN2	ASLN22322DN2 *		
					Incandescent	Transformer	ASLN2322N2	ASLN21322N2	ASLN22322N2 *		

• Color Code and Operating Voltage Code


LED Illuminated Type	Incandescent Illuminated Type	② Operating Voltage Code				
② Lens/LED Color Code	② Lens Color Code	③ Operating Voltage Code				
Specify a lens/LED color code in place of ② in the Type No. A: amber G: green R: red S: blue W: white Y: yellow	Specify a lens color code in place of ② in the Type No. A: amber G: green R: red S: blue W: white	Specify an operating voltage code in place of ③ in the Type No. 16: 100/110V AC 156: 115V AC 136: 120V AC 26: 200/220V AC 236: 230V AC 256: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC (incandescent only)				

- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer type contains an LED lamp (LSTD-62, rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp (LS-6, rated voltage 6V AC/DC).
- ullet On the 2-position selector switches marked with st above, the contact operation is reversed as follows.




Contact Block Mounting Position and Contact Arrangement Chart





• Dimensions



Illuminated Selector Switches

45° 3-position

Contact	Conta Bloc			oera:		Lamp	Maintained	Spring Return from Right	Spring Return from left	Spring Return Two-way
Code	Mounting Position	Туре	L	L C R		Input Type	L R	L R	LR	L R
	1	NO	•			Without Lamp Full Voltage	ASLN39920N2	ASLN319920N2	ASLN329920N2	ASLN339920N2
20 (2NO)	2	NO			•	LED Transformer	ASLN3@20DN@	ASLN31320DN2	ASLN32320DN2	ASLN33320DN2
						Incandescent Transformer	ASLN3320N2	ASLN31320N2	ASLN32320N2	ASLN33320N2
	1	NC		_		Without Lamp Full Voltage	ASLN39902N2	ASLN319902N2	ASLN329902N@	ASLN339902N2
02 (2NC)	2	NC				LED Transformer	ASLN3302DN2	ASLN31302DN2	ASLN32302DN2	ASLN33302DN2
						Incandescent Transformer	ASLN3302N2	ASLN31302N2	ASLN32302N2	ASLN33302N2
	1 2	NO NO	•		•	Without Lamp Full Voltage	ASLN39922N2	ASLN319922N2	ASLN329922N2	ASLN339922N2
22 (2NO-2NC)	3	NC NC				LED Transformer	ASLN3322DN2	ASLN31322DN2	ASLN32322DN2	ASLN33322DN2
	-					Incandescent Transformer	ASLN3322N2	ASLN31322N2	ASLN32322N2	ASLN33322N2
	1 2	NO NO	•		•	Without Lamp Full Voltage	ASLN39940N@	ASLN319940N@	ASLN329940N2	ASLN339940N2
40 (4NO)	3	NO NO	•		•	LED Transformer	ASLN3340DN2	ASLN31340DN2	ASLN32340DN2	ASLN33340DN2
						Incandescent Transformer	ASLN3340N2	ASLN31340N2	ASLN32340N2	ASLN33340N2
	1 2	NC NC				Without Lamp Full Voltage	ASLN39904N@	ASLN319904N@	ASLN329904N@	ASLN339904N2
04 (4NC)	3	NC NC			-	LED Transformer	ASLN3@04DN@	ASLN31304DN2	ASLN32304DN2	ASLN33304DN2
						Incandescent Transformer	ASLN3304N2	ASLN31304N2	ASLN32304N2	ASLN33304N2


Color Code and Operating Voltage Code

LED Illuminated Type	Incandescent Illuminated Type	© Operating Voltage Code			
② Lens/LED Color Code	② Lens Color Code	③ Operating Voltage Code			
Specify a lens/LED color code in place of ② in the Type No.	Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No. 16: 100/110V AC			
A: amber G: green R: red S: blue W: white Y: yellow	A: amber G: green R: red S: blue W: white	156: 115V AC 136: 120V AC 26: 200/220V AC 236: 230V AC 256: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC (incandescent only)			


- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp (LSTD-6@, rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp (LS-6, rated voltage 6V AC/DC).

• Contact Block Mounting Position and Contact Arrangement Chart





• Dimensions



Ring Operator Type / Lever Operator Type Selector Pushbuttons

Shape Contact Code							Ring/	Lever				
ABN	Shape					(F						Color
ABN A 1 NO							Pushl	outton		Type No	Type No	
A 2 NC				Mounting Position	Туре	Normal	Push	Normal	Push	туре но.	туре по.	
11	ABN		Α	-			•		•	ABN6111①	ABN6L111①	
Control Cont	TO GO					-						
Second S			I			•				ABN6411①	ABN6L411①	
Section ABN91110 ABN91110 ABN91110 ABN91110 ABN91110 ABN911110 ABN91120 ABN91120 ABN91120 ABN91120 ABN911220 ABN		(INO-INC)			_		•		_			
Ring Operator (90° 2-position) Mas Terminal Screw			G		_		Blocked		_	ABN9111①	ABN9L111①	
No No No No No No No No		20					•					
1	1 , , , , ,		D						•	ABN7120①		
B 3 NO	M3.5 Terminal Screw Panel Thickness 0.8 to 7.5 (including namplate)			1	NC	•						
## NO			B	2	NC	•				↑ PN6122①	ARNEL 1220	
1							•		•	ADINOTZZ	ABNOLIZZ	
ABN6222 ABN6L222 ABN6L222 ABN6L222 B: black G: green R: red Y: yellow ABN7L122 ABN7L122 ABN7L122 ABN7L122 ABN7L122 ABN7L122 ABN7L222	6 23 41 25						•		•			
ABN6222 ABN6L222 ABN6			С			•						
ABN6422① ABN6422① ABN6422① ABN6422① ABN6422① ABN6422① ABN6422① ABN6422② ABN6422② ABN6422② ABN7122②	WS.5 Terriminal Sciew									ABN6222①	ABN6L222①	
ABN*L 2 NC							•			-		
ABN*L 1 2 NC 0					_				•			
ABN6422① ABN6L422① R: red Y: yellow 1	1		ı		_					ABN6422①	ABN6L422①	
Y: yellow Y: y	ABN*L								_			
1									_			
22 NC ABN71220 ABN7L1220						•						
Cano-2nc		22	_					•		A DN 7400@	ADNIZI 400®	
1 NC ABN72220 ABN7L2220			D	3	NO		•			ABN/1220	ABN/L1220	
Lever Operator (90° 2-position) M3.5 Terminal Screw Panel Thickness 0.8 to 7.5 (including namplate) F 2 NC ABN7222① ABN71222①	W @ (6			4	NO				•			
ABN71221 ABN712221 ABN71	LIGIED -											
3 NO 4 NO 4 NO 5 23 41 26 3 NO 5 4 NO 6 6 NO	M3.5 Terminal Screw Panel Thickness 0.8 to 7.5		Е							ABN7222①	ABN7L222①	
1 NC	(including namplate)		_				•					
F 2 NC ABN71322① ABN7L322① ABN7L322① ABN7L322① ABN9L122① ABN9L122① ABN9L122①	1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1								•			
ABN713220 ABN7L3220 ABN7								•		_		
M3.5 Terminal Screw			F		_	•				ABN7322①	ABN7L322①	
1 NC • Blocked • ABN9122① ABN9L122①							-		•	-		
H 2 NC Blocked ABN9122① ABN9L122①	(including namplate)					•		•	_			
H 3 NO Blocked ABN9122(1) ABN9122(1) ABN9122(1)	□ mai pi 씨 ((- -)+)+ 원					Rlocked				ABN9L122①		
 			H				•	•	ABN9122①			
									•	1		

- Specify a button color code in place of ① in the Type No.
- Ring/Lever (metal): Chrome-plated

- 1. Circuit Codes A, B, C, and I: When the ring or lever operator is turned, the button is pushed in.
- 2. Circuit Codes E and F: The right and left NC contact blocks on circuit code E or F may overlap each other while turning the ring or lever operator. The NO and NC contact blocks on circuit code F may overlap each other while pressing the button.
- 3. Circuit Codes G and H: The pushbutton does not operate when the ring or lever operator is turned to the left position.
- 4. When using the selector pushbutton, do not turn the ring or lever operator with the pushbutton depressed. Otherwise, damage or failure may be caused.

• Contact Block Mounting Position and Contact Arrangement Chart



	Normal	Push
1	•	
2	•	
3		•
4		•

Mounting Hole Layout







ø30 ARN/ARNS series Mono-lever Switches

Single lever offers up to four directions of control

Mono-lever switches operate in four directions using a single lever. Switch contacts are actuated in the direction in which the lever is pushed, enabling quick and accurate control in any desired direction. Ideal for machine tools and industrial machines. The lever action can be maintained or spring-returned in any combination.

Also available with interlock mechanism to prevent inadvertent actuation.



Specifications and Ratings

Contact Ratings

Contact Block	Type BR
Rated Insulation Voltage	600V
Rated Continuous Current	10A
Contact Ratings by Utilization Category IEC 60947-5-1	AC-15 (A600) DC-13 (P600)

Characteristics

Contact Ratings by Utilization Category

Operational V	24V	48V	50V	110V	220V	440V			
Operational AC 50/60 Hz	AC	AC-12	AC-12 Control of resistive loads and solid state loads		_	10A	10A	6A	2A
	50/60 Hz	AC-15	Control of electromagnetic loads (> 72 VA)		_	7A	5A	3A	1A
Current	DC	DC-12	Control of resistive loads and solid state loads	10A	5A	_	2.2A	1.1A	_
	DC	DC-13	Control of electromagnets	4A	2A	_	1.1A	0.6A	_


Note: The operational current represents the classification by making and breaking currents (IEC 60947-5-1).

Specifications

	Double-break slow action
Contact Arrangement	Each contact block contains two independent contacts (2NO, 1NO-1NC, or 2NC)
	Up to four contact blocks can be mounted
Insulation Resistance	100 MΩ minimum (500V DC megger)
Dielectric Strength	Between live and dead parts: 2,500V AC, 1 minute
Mechanical Life	500,000 operations minimum
Electrical Life	(Interlocking type: 250,000 operations minimum)
Operating Temperature	−25 to +50°C (no freezing)
Operating Humidity	45 to 85% RH (no condensation)
Lever Knob	Black

BR Contact Block

The contact block is made of nylon resin. Each contact block contains two pairs of double-break silver contacts. There are three types as shown in the diagram below and up to four contact blocks can be mounted in any direction. A wide variety of circuits allows diverse combinations of control.





Control Mechanism

When the operator lever is pushed to about 30° in each direction from the neutral position, the contact in that direction activates. The lever can operate in two, three, or four directions, and combinations of maintained or spring-return from any position are possible.


ø30 ARN/ARNS series Mono-lever Switches

Types

Operator Type	Position	Lever Action	Type No.	Dimensions (mm)			
ARN (Long Lever Type)	2-position	Maintained	ARN2-1010-@B	M3.5 Terminal Screw Panel Thickness 0.8 to 6			
	(Up-Down)	Spring return	ARN2-2020-@B				
	2-position	Maintained	ARN2-0101-@B				
	(Left-Right) Spring return ARN2-0202-@B						
	4-position	Maintained	ARN4-1111-@B	1 block: 47, 2 blocks: 70 3 blocks: 93, 4 blocks: 116			
	(Up-Down-Left-Right)	Spring return	ARN4-2222-@B	Minimum horizontal/vertical mounting centers: 110			
ARNS (Short Lever Type)	2-position	Maintained	ARNS2-1010-@B	M3.5 Terminal Panel Thickness Screw 0.8 to 61			
	(Up-Down)	Spring return	ARNS2-2020-@B	Soletin Manager 18 and			
	2-position	Maintained					
	(Left-Right)	Spring return	ARNS2-0202-@B	63 51			
	4-position	Maintained	ARNS4-1111-@B	1 block: 47, 2 blocks: 70 3 blocks: 93, 4 blocks: 116			
	(Up-Down-Left-Right)	Spring return	ARNS4-2222-@B	Minimum horizontal/vertical mounting centers: 70			
ARNL (Interlocking Type)	2-position	Maintained	ARNL2-1010-@B	M3.5 Terminal Screw Panel Thickness 0.8 to 6			
	(Up-Down)	Spring return	ARNL2-2020-@B				
	2-position	Maintained	ARNL2-0101-@B				
THE ROLL	(Left-Right)	Spring return	ARNL2-0202-@B	6 23 83 51			
	4-position	Maintained	ARNL4-1111-@B	1 block: 47, 2 blocks: 70 3 blocks: 93, 4 blocks: 116			
The operator lever is locked only in the center position.	(Up-Down-Left-Right)	Spring return	ARNL4-2222-@B	Minimum horizontal/vertical mounting centers: 110			

- Specify Contact Arrangement from the table below in place of ④.
- Terminal covers are ordered separately.


• Lever Operator Position



Panel Cut-Out



Mono-Lever with Terminal Cover



Ordering Information

When ordering, specify items ${\scriptsize \textcircled{1}}$ to ${\scriptsize \textcircled{6}}$ according to the following example.

① Type	② No. of Contact Blocks ③ Lever Action		Contact Arrangement	© Lever Knob Color
ARN ARNS ARNL	1: 1 block 2: 2 blocks 3: 3 blocks 4: 4 blocks	Order of Entry: Up→Right→ Down→Left 1: Maintained 2: Spring return 0: Blocked	Order of Entry: Up→Right→ Down→Left 10: 1NO 01: 1NC 11: 1NO-1NC 20: 2NO 02: 2NC 00: Blocked	B: black

		Dire	ation					
Position		+		Contact Block				
ontact Block	Deptition of the control of the cont						Type	
ŏ	<u>1</u>	1	0	1	2	Terminal No		
1	1	NO	-	-	-	2	BR-2E	
'	3	_	_	NC	_	4	DK-ZE	
2	5	-	NO *	-	-	6	BR-1E	
-	7	-	-	-	NO	8	DK-1E	
3	9	NO	-	-	-	10	חם מד	
3	11	-	-	NC	_	12	BR-2E	
4	13	_	NC *	-	-	14	BR-3E	
4	15	_	-	-	NC	16	DK-3E	

- *: Contacts marked with * do not operate.
- To calculate the number of contact blocks required, add the number of NO and NC contacts on each pair of adjoining positions (up + right, right + down, down + left, and left + up). The largest of the four sums is the number of contact blocks required. Up to four contact blocks can be mounted.
- When UL and CSA markings are required on the mono-lever switch, specify as shown below. [Example] ARN4-1012-20000211-B-U



ARN/ARNS Series Mono-lever Switches **Ø30**

Accessories and Maintenance Parts

Shape	Specification	Type No.	Ordering Type No.	Package Quantity	Description
Nameplate	70	MLO	MLO	1	Chrome-plated brass
Пашерые	02	INIEO	MLOPN10	10	(matte surface)
Terminal Cover		ARN-VL2	ARN-VL2	1	Terminal covers are ordered separately. When ordering, specify the Type No. and the required quantity. Order 2 pieces for each contact block.
	() () () () () () () () () ()	BR-1E	BR-1E	1	2NO contact
Contact Block (BR Type)		BR-2E	BR-2E	1	1NO-1NC contact
		BR-3E	BR-3E	1	2NC contact
Bellows	Cago.	ARN-BL	ARN-BL	1	• For ARN/ARNS (Locking ring not included)
Bellows (Interlocking Type)		ARNL-BL	ARNL-BL	1	• For ARNL (Locking ring not included)
Knob	•	ARNB-①	ARNB-①	1	Specify a color code in place of ①. B (black), G (green), R (red) For ARN/ARNS

ø30/ø25 CS Series Cam Switches

76 standard circuits to choose from

- Wide variety of heavy-duty oiltight cam switches
- Operators available up to 12 positions
- Switches made with a double-pole contact block
- Contact blocks rated at 600V, 10A
- Ideal for ammeter/voltmeter applications
- UL listed and CSA approved



Specifications and Ratings

Contact Ratings

Rated Insulation Voltage	600V
Rated Continuous Current	10A
Contact Ratings by Utilization Category IEC 60947-5-1	AC-15 (A600) DC-13 (P600)

Characteristics

Contact Ratings by Utilization Category

Operational Voltage				24V	110V	220V	440V
	AC	AC-12	Control of resistive loads and solid state loads	_	10A	6A	2A
Operational	50/60 Hz	AC-15	Control of electromagnetic loads (> 72 VA)	_	5A	3A	1A
Current	Surrent DC DC		Control of resistive loads and solid state loads	8A	3A	1A	0.4A
DC		DC-13	Control of electromagnets	5A	1.2A	0.45A	0.2A

Note: The operational current represents the classification by making and breaking currents (IEC 60947-5-1).

Specifications

Contact Arrangement	Double-break slow action contacts Two contacts in one deck Up to 6 decks available (Spring-return type: Up to 3 decks)					
Operation	Maintained Spring return					
Angle	30°, 45°, 60°, 90°	45°				
Operator Positions	2 to 12	2, 3, 4				
Insulation Resistance	100 MΩ (500V DC megger)					
Dielectric Strength	2500V AC, 1 minute (between	live and dead parts)				
Mechanical Life	1 to 3 decks: 500,000 operations 4 to 6 decks: 200,000 operations					
Electrical Life	500,000 operations minimum					
Operating Temperature	-20 to +50°C (no freezing)					

CBS Contact Block

The CBS contact block contains two poles of double-break contacts. The contacts are operated by a cam designed to perform a required contact operation. Up to six contact blocks can be mounted on a maintained-action operator base, and up to three contact blocks on a spring return operator base.




Types


1 y pes	ype	@ Cantant			© Carian		⑦ Contact	Nama
ø30 Series	ø25 Series	© Contact Block Decks	③ Positions	Angle	⑤ Spring Return	Handle	Arrange- ment	Name- plate
ACSNO	ACSSO				0 : .	Y2, S2, P2,		
		Maintained: 1 to 6 decks Spring return: 1 to 3 decks	Maintained: 2 to 12 positions Spring return: 2 to 4 positions	Maintained: 30°, 45°, 60°, 90° Spring return: 45° only	Spring return from right Spring return from left Spring return two-way	F2, 25S2 (25S2 is for ACSSO only) (one speci- fied handle supplied)		See
(Photo: ACSNO with Y2 ha	ACSSK							page 56. (ordered
Standard Key (2 keys supp	H2 Handle Key (black)	Maintained: 1 to 6 decks Spring return: 1 to 3 decks	Maintained: 2 to 8 positions Spring return: 2 to 4 positions	Maintained: 45°, 90° Spring return: 45° only	Spring return from right Spring return from left Spring return two-way	Two standard keys are supplied. When the H2 key handle is required, specify H2.	See page 51.	sepa- rately)
UCSQO (Photo: With Y2 handle)	(Enclosed Type)	Maintained: 1 to 6 decks Spring return: 1 to 3 decks	Maintained: 2 to 12 positions Spring return: 2 to 4 positions	Maintained: 30°, 45°, 60°, 90° Spring return: 45° only	Spring return from right Spring return from left Spring return two-way	Y2, S2, F2, P2		Type CQ See page 56.
UCSQM	(Enclosed Type)					(one speci- fied handle	C1007	
	Indicator Left: Green Right: Red Left Wight Spring Return 2-way	Spring return: 1 to 3 decks	Spring return: 3 positions	Spring return: 45° only	Spring return two-way	Supplied) C1008 C1009 C1010 C1018 C2006 C2007 C2021 See page 51.		Type CQM See page 56.

• For handles and accessories, see page 49.

Dimensions



• Minimum horizontal/vertical mounting centers With P2 handle: 125 With other handles:



ø30/ø25 CS Series Cam Switches

Ordering Information

When ordering, specify items 1 through 2 as the designation example below.

1	2	3	4	(5)	6	7
Туре	Contact Block Decks	Positions	Angle	Spring Return	Handle	Circuit No.

	(1)	2		3		4)	5		6	7)
	U	Decks	Code	Positions	Code	Angle	Code	Return	Code		U U
A(A(U	CSNO CSNK CSSO CSSK CSQO CSQM	1 deck 2 decks 3 decks 4 decks 5 decks 6 decks	1 2 3 4 5 6	2 positions 3 positions 4 positions 5 positions 6 positions 7 positions 8 positions 9 positions 10 positions 11 positions 12 positions	2 3 4 5 6 7 8 9 10 11	30° 45° 60° 90°	3 4 6 9	Spring return from left Spring return from right Spring return two-way	RO OR RR	(Code) Y2, S2, P2, F2, H2, 25S2 (Color) B: Black See table below.	For standard contact arrangements, use des- ignation code on pages 51 to 53. For custom contact arrangements, use the Custom Contact Arrangement Specifica- tion Sheet on page 54.
		Spring retur 1 to 3 decks		Spring return: 2 to 4 position		ACSNK// 45° and 9 Spring re 45° only	90° only	Spring return c required only for return types.		25S2 is for ACSSO only.	

• Designation Example

- 1. When a special contact arrangement is required, specify the contact arrangement using the Custom Contact Arrangement Specification Sheet on page 54.
- 2. A specified handle is attached.
- 3. Accessories such as nameplates and jumpers are separately ordered.
- The key of the key operated cam switch is removable from every position. Specify other key removable configurations if required.

• Handle Designation Code

Shape	Code	Color	Applicable Cam Switch
Ø30 Y Handle	Y2		ACSNO UCSQO
ø30 S Handle	S2		UCSQM
Ø25 S Handle 20 30 30	25\$2	B: black	ACSSO
Ø30 P Handle	P2	D. DIACK	ACSNO UCSQO
ø30 F Handle	F2		UCSQM
Key Handle	H2		ACSNK ACSSK

Spring Return Operation

Available combinations of operator positions, angles, and return directions are listed in the table below.

Positions	2-po	sition	3-position			4-po:	3-position		
	From Left	From Right	From Left	From Right	Two-way	From Left	From Right	Two-way	
Return Direction	1_2	1 2	1 3	1 2 3	1 2 3	1 3	2 3 4	1 2 3	
3 4 5 Codes	24RO	24OR	34RO	34OR	34RR	44RO	440R	34RR	
Applicable Cam Switches	ACSNO, ACSSO, ACSNK, ACSSK, UCSQO UCSQM							UCSQM	
Contact Block Decks		1 to 3 decks							

Note: Maintained types do not require spring return code ⑤.




Accessories and Replacement Parts

SI	Shape			Ordering Type No.	Package Quantity	Remarks
Jumper CJ-1	P. Cuc		CJ-1	CJ-1PN10	10	For connecting terminals of adjoining contact blocks
CJ-2	The state of the s	Metal	CJ-2	CJ-2PN10	10	For connecting terminals of the same contact block
Rubber Boot		Rubber	CR-1	CR-1	1	For preventing ingress of dust into the contact blocks Not applicable for the UCSQO and UCSQM
Terminal Cover	Supplied with 2 self- tapping screws for mounting	Plastic	CS-VL2-13S	CS-VL2-13S	1	For 1 to 3 decks of contact blocks
CS-VL2-13S			CS-VL2-46S	CS-VL2-46S	1	For 4 to 6 decks of contact blocks

Shape	Material (Color)	Type No.	Ordering Type No.	Package Quantity
Ø30 Y Handle	Plastic (Black)	CSH-YB	CSH-YB	1
Ø30 S Handle	Plastic (Black)	CSH-SB	CSH-SB	1
Ø25 S Handle 25.6 20 30	Plastic (Black)	CSH-25SB	CSH-25SB	1
Ø30 P Handle	Plastic (Black)	CSH-PB	CSH-PB	1
Ø30 F Handle 30 € 40 Ø50	Plastic (Black)	CSH-FB	CSH-FB	1
Key Handle	Plastic (Black)	CSH-H2B	CSH-H2B	1
Handle Shaft	Plastic	CS-HF2C	CS-HF2CPN05	5
Handle Screw	For Y, Ø30 S, and Ø25 S handles M3 × 12	CS-SCW-M3-12	CS-SCW-M3-12PN10	10
Handle Screw	For P and F handles M3 × 25	CS-SCW-M3-25	CS-SCW-M3-25PN10	10


Installing the Terminal Cover for the CS series Cam Switches

- Complete wiring before installing the terminal cover on the bottom plate of the contact block.
- The terminal cover has six holes. Of the four round holes at four corners, use two diagonal pair of holes to install the terminal cover. Either pair can be used.
- Insert the attached self-tapping screws into the pair of holes and tighten the screws to a torque of 0.8 to 1.0 N·m.
- For 1 through 3 decks of contact blocks, use terminal cover CS-VL2-13S.
- For 4 through 6 decks of contact blocks, use terminal cover CS-VL2-46S.
- The CS-VL2-46S consists of the CS-VL2-13S and a terminal cover for the fourth through sixth decks. Combine the two parts together as shown. Note that once combined, the two parts cannot be separated.




For 1 through 3 decks of contact blocks (CS-VL2-13S)

Minimum Mounting Centers for Installing the Terminal Cover





Although the minimum mounting centers are 100 mm horizontally and 70 mm vertically, determine the mounting centers in consideration of convenience of wiring. For the P2 handle, the minimum mounting centers are 125 mm horizontally and vertically.



For 4 through 6 decks of contact blocks (CS-VL2-46S)

Terminal Cover Dimensions






All dimensions in mm.

Standard Contact Arrangements

- The following table lists 76 standard contact arrangements for easy designation of required cam switch operation.
- When other contact arrangements are required, specify the number of contact block decks, operator positions, angles, and contact operation using the Custom Contact Arrangement Specification Sheet on page 54.




Symbol	Contact Operation
•	Contacts closed.
_	Contacts remain closed between two operator positions.
##	Overlapping Contacts Contacts of different decks are both closed at one point while the handle is turned to the next position.
0	Residual Contacts When the handle is returned to the center, the contacts remain closed. The contacts are opened when the handle is turned to the opposite direction.

• Listing Order of the Table

The 76 standard contact arrangements are listed in the order of the circuit number.


Same Circuits

Shown in the following examples, circuits of Fig. 1 and Fig. 2 have the same functions. When ordering, examine the standard contact arrangements. Your requirements may be satisfied simply by changing external wiring of the standard contact arrangments.



• Terminal Numbers


The terminal numbers on the contact blocks correspond with the numbers shown in the chart as shown below.




	Standard Contact Arrangement Chart									
1 2 9 C1001	1 2 9 C1002	1 2 4 OR C1003	1 2 4 OR C1004	1 3 4 C1005						
3 4 4 1 2 1 2	3 4 4 1 2 1 2	3	3	3 4 1 2 3						
1 3 4 C1006	1 3 4 RR C1007	1 3 4 RR C1008	1 3 4 RR C1009	1 3 4 RR C1010						
3 4 1 2 3	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	$ \begin{array}{c c} 3 & & & 4 \\ 1 & & & 2 \\ & & 1 \rightarrow 2 \leftarrow 3 \end{array} $	$ \begin{array}{c c} 3 & & 4 \\ 1 & & 2 \\ & & 2 \end{array} $	$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$						
1 4 4 C1011	1 2 9 C1013	1 2 9 C1014	1 2 4 OR C1015	1 3 4 C1016						
3 4 4 1 2 3 4	3 4 1 2	3 4 1 2	3 4 1 2	3 4 4 2 1 2 3						
1 2 4 C1017	1 3 4 RR C1018	1 2 6 C1019								
3 4 4 1 2 2	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	3 4 1 2								
2 2 9 C2001	2 2 9 C2002	2 3 4 C2003	2 3 4 C2004	2 3 4 C2005						
7 8 5 6 3 4 1 2	7 - 8 5 - 6 3 - 4 1 - 2	7 - 8 8 6 3 4 4 1 - 2 3	7 — 8 5 — 6 3 — 4 1 — 2	7 - 8 5 - 6 3 - 4 1 - 2 1 2 3						

Ø30/Ø25 CS Series Cam Switches

		_		
2 3 4 RR C2006	2 3 4 RR C2007	2 4 4 C2008	2 4 4 C2009	2 4 9 C2011
7 - 8 6 5 - 6 4 1 - 2 1 - 2 - 3	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	7 8 6 3 4 1 2 3 4	7 8 6 6 3 4 1 2 3 4	7
2 2 9 C2014	2 2 9 C2015	2 3 4 C2016	2 3 4 C2017	2 3 4 C2018
7 — 8 5 — 6 3 — 4 1 — 2	7 8 5 6 3 4 1 2	7 8 6 3 4 4 1 2 3	7 8 5 6 3 4 1 2 3	7 - 8 5 - 6 3 - 4 1 - 2 1 2 3
2 3 4 C2019	2 3 4 C2020	2 3 4 RR C2021	2 4 4 C2022	2 3 3 C2023
7 — 8 5 — 6 3 — 4 1 — 2 1 2 3	7 - 8 5 - 6 3 - 4 1 - 2 1 2 3	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	7	7 8 6 6 3 4 1 2 3
2 3 3 C2024	2 4 3 C2025	2 5 3 C2027	2 3 6 C2028	2 3 6 C2029
7 - 8 5 - 6 3 - 4 1 - 2 1 2 3	7 8 8 6 3 4 4 1 2 3 4	7 8 6 6 3 4 1 2 3 4 5	7 8 5 6 3 4 1 2 3	7 8 6 6 3 4 1 2 1 2 3 (R) (S) (T)
3 2 9 C3001	3 3 4 C3002	3 5 4 C3003	3 6 4 C3004	3 3 4 C3005
11 12 9 10 7 8 5 6 3 4 1 2	11	11 12 9 10 7 8 5 6 3 4 1 2 1 2 3 4 5	11 12 12 10 7 8 8 5 6 6 3 4 4 1 2 3 4 5 6	11 12 9 10 7 8 8 5 6 3 4 4 1 2 3
3 4 9 C3008	3 4 9 C3009	3 2 9 C3010	3 3 4 C3011	3 4 4 C3012
11 12 9 10 7 8 5 6 3 4 4 1 2 3 4 (O) (RS) (ST) (TR)	11 12 9 10 7 8 5 6 3 4 4 1 2 3 4	11 12 9 10 7 8 5 6 3 4 1 2	11 12 9 10 7 8 5 6 3 4 4 1 2 3	11 12 12 9 10 7 8 8 5 6 6 3 4 4 1 2 3 4
3 6 3 C3013	3 3 6 C3014	3 6 6 C3015	3 5 3 C3016	3 4 4 C3017
11 12 9 10 7 8 8 5 6 6 3 4 4 1 2 2 1 2 3 4 5 6	11 12 9 10 7 8 5 6 3 4 1 2 3	11 12 12 10 7 8 5 6 6 3 4 1 2 3 4 5 6	11 12 12 10 7 8 8 5 6 3 4 4 1 2 1 2 3 4 5	11 12 9 10 7 8 5 6 3 4 4 1 2 3 4
3 3 6 C3018	3 3 6 C3019	4 4 4 C4001	4 8 4 C4002	4 4 9 C4003
11 12 9 10 7 8 8 5 6 6 3 4 1 2 2 1 2 3	11 - 12 9 - 10 7 - 8 5 - 6 3 - 4 1 - 2	15	15	15 16 16 13 14 11 12 9 10 7 8 8 5 6 6 3 4 1 1 2 3 4 (O) (R) (S) (T)
4 2 4 C4004	4 2 9 C4005	4 2 9 C4006	4 4 9 C4007	4 3 4 C4008
15	15 16 13 14 11 12 9 10 7 8 5 6 3 4 1 2	15 16 13 14 11 12 9 10 7 8 5 6 3 4 1 2	15 16 16 17 14 11 12 12 12 10 10 7 10 7 10 7 10 7 10 7	15




Application Examples (Voltmeter and Ammeter Circuits)



Custom Contact Arrangement Specification Sheet

- The preceding pages provide 76 standard contact arrangements. When other contact arrangements are required, specify the number of contact block decks, operator positions, angles, and contact operation using the Custom Contact Arrangement Specification Sheet shown below.
- For available number of contact blocks and operator positions, see the Ordering Information on page 48.
- 1. Specify operator positions


Indicate the operator positions starting at the first position. When spring return operation is required, mark an arrow between two operator positions to indicate the spring return direction.



2. Specify contact operation at each operator position Indicate the required operation of all contacts at each operator position using the following symbols.

Symbol	Contact Operation
•	Contacts closed.
-	Contacts remain closed between two operator positions.
+++	Overlapping Contacts Contacts of different decks are both closed at one point while the handle is turned to the next position. Overlapping contacts are not available for handle angles of 30° and 45°.
0::::•	Residual Contacts When the handle is returned to the center, the contacts remain closed. The contacts are opened when the handle is turned to the opposite direction.

• One deck of contact block contains two poles of contacts and four terminals. When the handle is made to turn 180° or more, special attention is needed. Since one cam operates the two poles of contacts on opposite positions, the same contact operation repeats on the other pole of contacts when the handle is turned 180°. When different contact operation is needed for handle angles of 180° or more, use another deck of contact block.



Accessories

	Terminal Cover	N-VL2	N-VL3	N-VL4	APN-PVL	APD-PVL	Use of termi- nal covers increases the
			母	16	4	4	depth by the dimensions below.
ø30 Series Control Unit		38.4H × 22W	38H × 30.4W	38.4H × 24W	38H × 46W	37H × 44W	Terminal Cover
Pilot Light APN, APNE, UPQN, UPQNE	F. III Valta va				X		+5.0 mm
Pilot Light APD, APDE	- Full Voltage					Х	+5.2 mm
Pilot Light APN, APNE, APD, APDE, UPQN, UPQNE	Transformer DC-DC Converter		х				+2.7 mm
Pushbutton	1 contact block Terminal Cover	Х					
ABN, ABD, AON, AOD, AVN, ABGD, AJN, ABFD, ATN, AOFD, UBQN, AVD, UOQN, AJD, UWQN, AZD, ABBN, AYD, ABBS (Ø25)	2 contact blocks	X 2 pieces					+0 mm
Selector Switch ASN, ASD, ASTN	3 contact blocks CB CB CB	X 2 pieces					70 111111
Selector Pushbutton ABN, ASBD	4 contact blocks CBICB CBICB	X 2 pieces					
Illuminated Pushbutton ALN, ALD, ALNE, ALDE, AOLN, AOLD, AOLNE, AOLDE, ALGN, ALGD, ALGNE, ALGDE, AOLGN, AOLGDE, ALFN, ALFD, ALFNE, ALFDE, AOLFN, AOLFD, AOLFNE, AOLFDE, AVLN, AVLD, AVLNE, AVLDE,	Full Voltage			X 2 pieces			+4.5 mm
AJLN, AJLD, AJLNE, AJLDE, ULQN, UOLQN Illuminated Selector Switch ASLN, ASLD Push-to-Check Pilot Light APN1**P	Transformer DC-DC Converter		х				+1.5 mm

• Ordering Terminal Covers

When ordering terminal covers, specify the Type No. and the quantity.

ø30 series Accessories and Replacement Parts

Nameplates

Туре	Legend	Material	Type No.	Ordering Type No.	Package Quantity	Dimensions (mm)	Applicable Unit
	Blank		NA-0	NA-0	1		
NA	Blam	Aluminium 1.2 mm thick		NA-0PN10	10		
INA	With Legend	White letters on black background	NA-*	NA-*	1	27.5	ø30 Control Unit
	With Legend		NA.	NA-*PN10	10		230 CONTROL CHIL
NALO	Blank	Aluminium 1.2 mm thick	NALO	NALO	1	19 8 40 19 12 19 19 19 19 19 19 19 19 19 19 19 19 19	
TWILE	Biank	Black		NALOPN10	10	1.5 A.	
MLO	Blank	Brass (chrome-plated)	MLO	MLO	1	170 4 4 (35) 82	ARN/ARNS Mono-Lever
INIEG	Biank	1.0 mm thick Matte	20	MLOPN10	10		
Blank	Blank	Aluminium 0.5 mm thick	CQ-0	CQ-0	1	With adhesive tapes on the back 2-03.5	UCSQO Cam Switch
CQ	Diam			CQ-0PN10	10		
Od	With Legend (Legend	White letters on black background legend and s 31	CQ-*	CQ-*	1	ø13 —20—	
	Codes 31 and 53 only)			CQ-*PN10	10		
	Blank		CQM-0	CQM-0	1	With adhesive tapes on the back	
CQM	Diam	Aluminium 0.5 mm thick	CQIVI-U	CQM-0PN10	10	12+	UCSQM Cam Switch
	With Legend (Legend	White letters on black background egend	CQM-*	CQM-*	1	2-ø3.5 ø13 40 □64	
	Code 31 only)			CQM-*PN10	10	1- — 🗆 🗝	

[•] Specify a legend code in place of * in the Ordering Type No.

Nameplates


Туре	Legend	Material	Type No.	Ordering Type No.	Package Quantity	Dimensions (mm)	Applicable Unit
	Blank		CQN-0	CQN-0	1	With adhesive tapes on the back	ACSNO, ACSNK Cam Switches ø30 mm Selector Switches
CQN	DIATIK	Aluminium 0.5 mm thick	CQIV-0	CQN-0PN10	10		
	With Legend (Legend	White letters on black background	CQN-*	CQN-*	1		
	Codes 31, 35, and 53 only)		CQN-*	CQN-*PN10	10		
	Blank	Aluminium 0.5 mm thick	CQS-0		1	With adhesive tapes on the back	
cqs	DIATIK		003-0	CQS-0PN10	10		ACSSO, ACSSK Cam Switches ø25 mm Selector Switches
	With Legend (Legend Code	nd Code	CQS-*	CQS-*	1		
	53 only)		CQ3-*	CQS-*PN10	10	<u>64</u>	
HNAV	Blank	k Polyamide Black letters on	HNAV-0	HNAV-0	1	ERGE NO.	HN1E ø30 mm series
	EMERGENCY	yellow back- ground	HNAV-27	HNAV-27	1	Legend "EMERGENCY STOP" is indicated outside a ø44mm circle.	Emergency Stop Switches

 $[\]bullet$ Specify a legend code in place of \ast in the Ordering Type No.

Legends

9-11-11-						
Code	Legend					
0	(blank)					
1	ON					
2	OFF					
3	START					
4	STOP					
31	OFF-ON					
35	HAND-AUTO					
53	HAND-OFF-AUTO					

Shape and Engraving Area



Example

Shape	ape Engraving Area Height Width		Engraving Are		Max. No.	No. of Letters
Snape			of Lines	on 1 Line		
Standard	5	36	1	14		
Large	10	36	2	14		

[•] The above example is when the letter is 4 mm tall.

Accessories

Shape		Material	Type No.	Ordering Type No.	Package Quantity	Dimensions (mm)
Locking Ring Wrench		Rubber	OR-12	OR-12	1	Used to tighten the locking ring when installing the ø30 or ø25 switch onto a panel. Output When the locking ring when installing the ø30 or ø25 switch onto a panel. Output Ou
Lamp Holder Tool		Rubber	OR-55	OR-55	1	Used to install and remove the LED/incandescent lamps. See page 64. ORASS ORASS TO ORASS
Contact Rubber Boot For momentary 1 layer of contact blocks (2 contact blocks)		Rubber (nitryl) (black)	OC-99	OC-99	1	Rubber boot used to prevent oil and dirt from entering into the contact block. Temperature range: -5 to +60°C Cannot be used for zinc diecast control units.
Contact Rubber Boot	For 1 layer of contact blocks (2 contact blocks)	Rubber	OC-90	OC-90	1	Applicable to AVN3 and AJN3. Applicable to ø30 diecast zinc pushbuttons and selector switches.
	For 2 layers of contact blocks (4 contact blocks)	(translucent)	OC-290	OC-290	1	42.8
Anti-rotation Ring		Metal	OGL-11	OGL-11PN10	10	Used to prevent the operator from turning. Generally used when using no nameplates on selector switches and selector pushbuttons. See page 64. 2.8 0.8 0.8
Rubber Mounting Hole Plug		Rubber (black)	OB-13B	OB-13BPN05	5	Used to plug unused ø30mm mounting holes. Gray also available. Ordering Type No.: OB-13PN05 OB-13PN05
Plastic Mounting Hole Plug		Plastic (gray)	OBP-11	OBP-11	1	Tightening torque: 1.2 N·m. Degree of protection: IP65 M30 P1.5 Screw Locking Ring
Metallic Mounting Hole	Plug	Metal (diecast) (zinc-plated)	OB-11	OB-11	1	Tightening torque: 1.2 N·m. Degree of protection: IP65 M30 P1.5 Screw Locking Ring Tightening torque: 1.2 N·m. Locking Ring

Accessories

Sh	Shape		Тур	e No.	Ordering Type No.	Package Quantity	Dimensions (mm)
Button Cover Extended Pus			Color	Туре	_	_	Metallic bezels cov- and with a without boot
Extended Pus	snouttons		Black	OC-11B	OC-11B		ered with a rubber boot to enhance waterproof
		Rubber (nitryl)	Green	OC-11R	OC-11R	-	characteristics. • Button is not included.
	2	, , ,	Red	OC-11G	OC-11G	1	Applicable to extended
			Yellow	OC-11Y	OC-11Y	-	pushbuttons only. M30 P1.5
Pushbutton							Used to cover and pro-
Clear Boot	For flush pushbuttons	Rubber (EPDM)	OC-121		OC-121	1	tect pushbuttons where units are subject to water splash. Not suitable for outdoor use or where the units are subject to oil splash.
	For extended pushbuttons	(=: 5.11)	OC-122		OC-122	1	A B OC-121 37 16 OC-122 37 16
Dust-proof Ru Jumbo Mushr	bber Cover for						Used for ABN4G
Jumpo Mushi	ooms	Rubber (nitryl) black	OC-4GN		OC-4GN	1	pushbuttons. Panel Thickness 1.2 to 5.5
Padlock Cove		Polyarylate (gasket: nitryl rubber)	OL-KL1		OL-KL1	1	Used to protect pushbuttons, illuminated pushbuttons, and selector switches (knob operator). Resultation Resultation Resultation Waterproof Rubber Gasket 0.5t 30
Metal Protecto	or Co	Metal (zinc-plated)	OL-C		OL-C	1	Used to protect flush pushbuttons from inadvertent operation. Can be easily attached using the locking ring. 42.5 42.5 11.5 1.6
Locking Attack	hment	Metal (zinc-plated)	OL-H		OL-H	1	Used to lock an extended pushbutton in the depressed position. Can be easily attached using the locking ring. Locking Plate Mounting Plate

ø30 ø30 Series Accessories and Replacement Parts

Maintenance Parts

Shape	Specification	Type No.	Ordering Type No.	Package Quantity	Remarks
Metallic Bezel	Metal (chrome-plated)	OG-11	OG-11PN02	2	
Plastic Bezel	Plastic	OGP-11*	OGP-11*PN02	2	Specify a color code in place of *. B (black), G (green), R (red), W (white), Y (yellow)
Clear Plastic Bezel for Flush Pushbuttons		OGP-13	OGP-13PN02	2	
Clear Plastic Bezel for Extended Pushbuttons	Clear Plastic	OGP-14	OGP-14PN02	2	Clear plastic bezel and full shroud. OGP-1411 cannot be used with LED illumination units and diecast units.
Clear Plastic Bezel for Illuminated Pushbuttons		OGP-1411	OGP-1411	1	
Clear Button Cover	Clear Plastic	ABN1B-C	ABN1B-CPN05	5	Used on flush and extended pushbuttons to indicate a mark or a symbol engraved on the marking plate. The clear button cover holds the marking plate. The ø30 series marking chip can
Marking Plate	Plastic	TN-0*	TN-0*PN10	10	plate. The #30 series marking chip can only be used on the ABN1 and AON1. Specify a color code in place of *. B (black), G (green), R (red), W (white), Y (yellow)

Maintenance Parts

Shape	Description	Mate- rial	Type No.	Ordering Type No.	Package Quantity		Color	
Contact Block (BS: Dark gray)	1NO contact		BS010E	BS010E	1	Push rod colo	r: Green	
	1NC contact		BS001E	BS001E	1	Push rod colo	r: Red	
	EM contact (early make)		BS010SE	BS010SE	1	Push rod colo	Push rod color: Black	
Par 18	LB contact (late break)		BS001SE	BS001SE	1	Push rod colo	r: White	
Contact Block (BST: Light gray)	1NO contact		BST010	BST010	1	Push rod color: Green	Applicable Units: • Pushlock Turn Reset • Push Turn Lock	
	1NC contact		BST001	BST001	1	Push rod color: Red	LED Illuminated Pushbutton LED Illuminated	
	EM contact (early make)		BST010S	BST010S	1	Push rod color: Black	Selector Switch Incandescent Illuminated Selector	
Ages All	LB contact (late break)		BST001S	BST001S	1	Push rod color: White	Switch • All ø30 Diecast Zinc Control Units	
Lens	Used for APN(E)1		APN106LN-2	APN106LN-@PN05	5	S (blue), W (wh Use the white illumination	(W) lens for pure white	
	Used for UPQNE4		UPQN406L-@	UPQN406L-@PN05	5		een), R (red), S (blue) (C) lens for white illumi-	
	U(O)LQN*B	Plastic	UPQN406LD-@	UPQN406LD-@PN05	3	A (amber), Y (ye • Use the amber illumination.	ellow) er (A) lens for orange	
	Used for		ULQN06L-@	ULQN06L-@PN05	_	C (clear), G (gre	een), R (red), S (blue)	
	UPQN3B U(O)LQN		UPQN06LD-@	UPQN06LD-@PN05	5	A (amber), W (white), Y (yellow) • Use the amber (A) lens for orange illumination.		
Lens	Used for		ALN2L-2	ALN2L-@PN05	5	G (green), R (re	ed), S (blue)	
	ALN, AOLN (LED)		ALN2LD-2	ALN2LD-@PN05	5	, , , ,	vhite), Y (yellow) (W) lens for pure white	
		Used for ALN. AOLN		ALN06L-@	ALN06L-@PN05	5	C (clear), G (gre	een), R (red), S (blue)
	(incandescent) (1W)	Plastic	ALN06LD-2	ALN06LD-@PN05	5	A (amber), W (v Use the amber illumination.	vhite) er (A) lens for orange	
	Used for ALN, AOLN		ALN08L-@	ALN08L-@PN05	5	C (clear), G (gre	een), R (red), S (blue)	
	(incandescent) (2W)		ALN08LD-@	ALN08LD-@PN05	5	A (amber), W (v Use the amberillumination.	vhite) er (A) lens for orange	
Button	Flush		ABN1B-①	ABN1B-①PN05	5	G (green), R (re	, , ,	
	Extended		ABN2B-①	ABN2B-①PN05	5	units (dark colo	re used for ø30 control red operator units).	
	Mushroom	Dioatio	ABN3B-①	ABN3B-①PN02	2	colored operato	lack buttons from light r units.	
Button	Flush	Plastic	ABN1BN-①	ABN1BN-①PN05	5		een), R (red), S (blue),	
	Extended		ABN2BN-①	ABN2BN-①PN05	5		e used for ø30 diecast	
	Mushroom		ABN3BN-①	ABN3BN-①PN02	2	zinc control unit units).	s (light colored operator	
Button	• Mushroom (ABN4)		ABN4B-①	ABN4B-①	1			
0 0	Mushroom (ABN4G/ABN4F)	Plastic	ABN4GB-①	ABN4GB-①	1	- B (black), G (gro	een), R (red), Y (yellow)	
8 0	Square Flush (UBQN1)		UBQN1B-①	UBQN1B-①PN02	2			
	SquareExtended(UBQN2)		UBQN2B-①	UBQN2B-①PN02	2			

Note: Specify a button color code or lens color code in place of ① or ② in the Ordering Type No.

ø30 ø30 Series Accessories and Replacement Parts

Maintenance Parts

Shape	Description	Material	Type No.	Ordering Type No.	Package Quantity	Remarks
Lens	For ø40 pushlock to pushbuttons	urn reset	AVLN3L-R	AVLN3L-RPN02	2	
Marking Plate	For UPQN4	Plastic	UPQN406N-W	UPQN406N-WPN05	5	
Spare Key	ASN*K	Metal	ASN-SK-24401	ASN-SK-24401PN02	2	Applicable to ABN3K, ABN4K, ABN5
Rubber Washer (3.0mm thick)		Rubber	OW-12	OW-12PN10	10	
Rubber Washer (1.5mm thick)		Rubber	OW-11	OW-11PN10	10	
Shroud	Half shroud (for pushbuttons)		ABN2G	ABN2G	1	
0 0	Full shroud (for pushbuttons)		ABN2F	ABN2F	1	
6	• Full shroud (for mushroom pushbuttons)		ABN3G	ABN3G	1	
9			ABN4G	ABN4G	1	
	Deep shroud (for jumbo mush- rooms)	Metal	ABN4F	ABN4F	1	
	Half shroud (for illuminated)		ALN1GL	ALN1GL	1	For incandescent/LED illuminated pushbuttons (E12 base)
	pushbuttons)		ALN2GL	ALN2GL	1	For LED illuminated pushbuttons (BA9S base)
	Full shroud (for illuminated		ALN1F	ALN1F	1	For incandescent/LED illuminated pushbuttons (E12 base)
	pushbuttons)		ALN2FL	ALN2FL	1	For LED illuminated push- buttons (BA9S base)
Transformer	100/110V AC (for LED/1W incand lamps)	descent	TWR-016N	TWR-016N	1	Mounting screws are not
Most Most	200/220V AC (for LED/1W incand lamps)	descent	TWR-026N	TWR-026N	1	included.

Maintenance Parts

LED Lamps

Dimensions	Operating	Curren	t Draw	Type No.	Ordering	Illumination	Package	Base
Dillicitations	Voltage	AC	DC	турс но.	Type No.	Color Code	Quantity	Dasc
	6V AC/DC ±10%	17 mA (A, R, W, Y)	14 mA (A, R, W, Y)	LSTD-62	LSTD-6@	Specify a color code in place of a in the Order-	1	
	0	8 mA (G, PW, S)	5.5 mA (G, PW, S)	LOTD 0	LSTD-6@PN10	ing Type No.	10	
Base BA9S/13	12V AC/DC ±10%	11 mA	10 mA	LSTD-12	LSTD-1@	A: amber G: green	1	BA9S/13
20.4	124 7(0/20 110/0	11111/	10 1111/1	2010 16	LSTD-1@PN10	PW: pure white R: red S: blue	10	
	24V AC/DC ±10%	11 mA	10 mA	LSTD-22	LSTD-2@	W: white Y: yellow	1	
	244 710/20 110/0	DC ±10% IT IIIA TO IIIA ESTO	2010 20	LSTD-2@PN10		10		
	6V AC/DC ±10%	17 mA (A, R, W, Y)	14 mA (A, R, W, Y)	LETD-62	LETD-6@	Specify a color code in place of ② in the Order-	1	
	0 10,00 110,0	8 mA (G, PW, S)	5.5 mA (G, PW, S)	ELID 0	LETD-6@PN10	ing Type No.	10	
Base E12/15	12V AC/DC ±10%	7 mA	6.5 mA	LETD-82	LETD-8@	A: amber G: green	1	E12/15
27	120 A0/00 110/0 / 111/A	0.0 111/1		22.15.0	LETD-8@PN10	R: red S: blue W: white	10	
	24V AC/DC ±10%	11 mA	10 mA	LETD-22	LETD-2@	Y: yellow	1	
	24 V 7.0/20 110/0	1111111	10 11111		LETD-2@PN10		10	

Incandescent Lamps

Dimensions	Rated Operating Voltage	Lamp Ratings	Type No.	Package Quantity	Life
Base BA9S/13	6V AC/DC	1W (6.3V)	LS-6		
	12V AC/DC	1W (18V)	LS-8	1	
22.5±1.5	18V AC/DC	1W (24V)	LS-2		Approx. 1000 hours minimum
1 7 6	24V AC/DC	1W (30V)	LS-3		
Base E12/15	6V AC/DC 2W (6.3V) LE-6 (reference value		(reference value)		
-	12V AC/DC	2W (18V)	LE-8	1	
34±2	18V AC/DC	2W (24V)	LE-2		
 < ···· > 	24V AC/DC	2W (30V)	LE-3		

Transformer

Separate Mounting Type	Primary Voltage	Secondary Voltage	Type No.	Applicable Load
For 1W	100/110V AC		TWR516	One full voltage type pilot light or illuminated
	200/220V AC	5.5V	TWR526	switch containing LSTD-62, LETD-62 LED lamp (6V AC/DC) or LS-6 incandescent
	400/440V AC		TWR546	lamp (6.3 V AC/DC, 1W)
For 2W	100/110V AC		TWR518	
	200/220V AC	15V	TWR528	One full voltage type pilot light or illuminated switch containing LE-8 incandescent lamp (18V AC/DC, 2W)
	400/440V AC		TWR548	, , ,

Safety Precautions

- Turn off the power to the ø30 series control units before starting installation, removal, wiring, maintenance, and inspection of the products. Failure to turn power off may cause electrical shocks or fire hazard.
- To avoid a burn on your hand, use the lamp holder tool when replacing lamps.
- For wiring, use wires of a proper size to meet the voltage and current requirements. Tighten the M3.5 terminal screws to a tightening torque of 1.0 to 1.3 N·m. Failure to tighten terminal screws may cause overheat and fire.

Instructions

Panel Mounting for Square Pushbuttons and Pilot Lights

- 1. Tighten the square ring to the operator and position the ring correctly.
- 2. Lightly tighten the screw to secure the pilot light onto the



Tightening Torque for Terminal Screws

Tighten the terminal screws to a torque of 1.0 to 1.3 N·m.

Replacement of Lamps

Lamps can be replaced by using the lamp holder tool (OR-55) from the front of the panel.

How to Remove

To remove, slip the lamp holder tool onto the lamp head lightly. Then push slightly, and turn the lamp holder tool counterclockwise.

How to Install

To install, insert the lamp head into the lamp holder tool. Place the pins on the lamp base to the grooves in the lamp socket. Inset the lamp and turn it clockwise.






Installing the Anti-rotation Ring

Anti-rotation rings are used on selector switches or pushbuttons which rotate and used when using no nameplates.

Insert a 1.5mm thick rubber washer between the panel and the anti-rotation ring as shown on the right.



Panel Thickness and Rubber Washer

Adjust the thickness of the rubber washers according to the panel thickness. Also, make sure to include the nameplate thickness when using a nameplate.

Applicable Models

- Extended Illuminated Pushbuttons with Half Shroud (LED)
- Extended Pushbuttons with Half Shroud (Diecast)
- Extended Illuminated Pushbuttons with Half Shroud (Diecast)

		,
Panel Thickness	Rubber	Washer
(mm)	1.5mm	3.0mm
Supplied	1 piece	1 piece
0.8 to 1.8	_	1 piece
1.8 to 3.5	1 piece	_

Applicable Models

- Extended Illuminated Pushbuttons with Full Shroud (Incandescent)
- Extended Illuminated Pushbuttons with Full Shroud (LED)
- Extended Illuminated Pushbuttons with Full Shroud (Diecast)
- . Mushroom Pushbuttons with Full Shroud

Panel Thickness	Rubber Washer		
(mm)	1.5mm	3.0mm	
Supplied	2 pieces	1 piece	
0.8 to 2.0	1 piece	1 piece	
2.0 to 3.5	1 piece	1 piece	
3.5 to 5.0	-	1 piece	
5.0 to 6.0 (6.5)	1 piece	_	

The number in brackets is for mushroom pushbuttons with full shroud. Extended illuminated pushbuttons with full shroud (incandescent) are 5.0 mm maximum.

Applicable Models

- Toggle Lever Types
- Knob Push Turn Lock Illuminated **Pushbuttons**

Panel Thickness	Rubber Washer		
(mm)	1.5mm	3.0mm	
Supplied	1 piece	1 piece	
0.8 to 2.0	1 piece	1 piece	
2.0 to 3.5	-	1 piece	
3.5 to 5.5 (5.0)	1 piece	-	

The number in brackets is for knob push turn lock illuminated pushbuttons

Applicable Models

- Extended Pushbuttons with Half Shroud
- Extended Illuminated Pushbuttons with Half Shroud (Incandescent)

Panel	Rubber Washer		
Thickness (mm)	1.5mm	3.0mm	
Supplied	1 piece	1 piece	
0.8	1 piece	1 piece	
0.8 to 2.3	-	1 piece	
2.3 to 4.0	1 piece	-	

Applicable Models

 Extended Pushbuttons with Full Shroud

Panel	Rubber Washer			
Thickness (mm)	1.5mm	3.0mm		
Supplied	3 pieces	1 piece		
0.8 to 1.5	3 pieces	1 piece		
1.5 to 3.0	2 pieces	1 piece		
3.0 to 4.5	1 piece	1 piece		
4.5 to 6.0	-	1 piece		
6.0 to 7.5	1 piece	-		

Applicable Models

· Extended Pushbuttons with Full Shroud (Diecast)

Panel	Rubber Washer			
Thickness (mm)	1.5mm	3.0mm		
Supplied	2 pieces	1 piece		
0.8 to 2.5	2 pieces	1 piece		
2.5 to 4.0	1 pieces	1 piece		
4.0 to 5.5	-	1 piece		
5.5 to 6.0	1 piece	_		

Applicable Models

· Other Models (Excluding Square

Types)				
Panel	Rubber Washer			
Thickness (mm)	1.5mm	3.0mm		
Supplied	2 pieces	1 piece		
0.8 to 3.5	2 pieces	1 piece		
3.5 to 5.0	1 piece	1 piece		
5.0 to 6.5	_	1 piece		
6.5 to 7.5	1 piece	-		



Installation of LED Illuminated Units

1. Note the polarity for wiring when connecting to DC-DC converter unit.

Terminal No.	Polarity
X1	Positive
X2	Negative

- 2. Transformer type units are recommended for use in areas subjected to noise.
- 3. Notes for Pure White LED Lamps
- Do not use the pure white LED outdoors, otherwise it will lead to the degradation of brightness and color. Do not remove or apply shock to the cap on the pure white LED lamp, otherwise it may break or damage the cap.
- For the pure white LED, use a white lens. The illumination color will be dull if a different color is used.

Notes on LED Illuminated Units

LED lamps consist of semiconductors. If the applied voltage exceeds the rated voltage, LED elements may deteriorate due to overheat, resulting in significant decrease in luminance, hue change, or failure of lighting. Also, if an extraneous noise, transient voltage, or transient current is applied to the circuit, similar effects may occur. When using LED lamps, observe the following instructions.

Rated Voltage

The LED lamps are rated at 6V, 12V, or 24V AC/DC, and can be used within ±10% the rated voltage of either AC or DC.

DC Power

- 1. Switching power supply Regulated voltage from switching power supply is best suited. Make sure to use within the rated voltage of the LED lamp.
- 2. Rechargeable battery


Note that the battery voltage may exceed the rated voltage of the LED lamp while the battery is being charged and immediately after the charging is complete. Be sure to use the LED lamp on a voltage of ±10% the rated voltage.


- 3. Full-wave rectification
 - Since the LED lamp is AC/DC compatible, a diode bridge for rectification is not necessary. If the LED lamp is used on a full-wave rectification current through a diode bridge, the rectifier diodes will reduce the voltage, resulting in lower luminance.
- 4. Single-phase half-wave rectification This is not suitable for the power source of LED lamps. Use constant-voltage DC power.

Noise


LED elements deteriorate due to extraneous noise, resulting in significant decrease in luminance, hue change, or failure of lighting. When such effects are anticipated, take a protection measure shown below, such as RC elements or a surge absorber.

[Protection Example 1] For AC circuit





[Protection Example 2] For DC circuit




Countermeasures against Dim Lighting

- 1. Leakage currents through the transistors or a contact protection circuit may cause the LED lamp to illuminate dimly even when the output is off.
- 2. When the LED lamp is illuminated by a transistor output, take the following measure.

[Circuit Example]

Connect shunt resistor R in parallel with the LED lamp.



R: Shunt resistor

ø30 | ø30 series Diecast Zinc Control Units

Heavy duty switches for tough industrial usage

- Degree of protection: IP65 (IEC 60529)
- UL, CSA approved, and EN compliant

Safety Standards	File No. or Organization
UL UL LISTED	UL Listing File No. E68961
CSA	File No. LR21451
EN EN60947-5-1	CE



Specifications and Ratings

Contact Ratings

Pushbuttons	Contact Block	Type BST (ø30 series)
Illuminated Pushbuttons	Rated Insulation Voltage	600V
Selector Switches	Rated Continuous Current	10A
Illuminated Selector Switches Selector Pushbuttons	Contact Ratings by Utilization Category IEC 60947-5-1	AC-15 (A600) DC-13 (P600)


Characteristics

• Contact Ratings by Utilization Category

Operational Voltage				24V	48V	50V	110V	220V	440V
	AC	AC-12	Control of resistive loads and solid state loads	10A	_	10A	10A	6A	2A
oporanoria:	AC-15	Control of electromagnetic loads (> 72 VA)	10A	_	7A	5A	3A	1A	
	DC-12	Control of resistive loads and solid state loads	10A	5A	_	2.2A	1.1A	_	
	DC	DC-13	Control of electromagnets	5A	2A	_	1.1A	0.6A	_

Note: The operational current represents the classification by making and breaking currents (IEC 60947-5-1). Minimum applicable load: 3V AC/DC, 5 mA (applicable range may vary with operating conditions and load types)

BST Contact Block (Light Gray)



Contact Block Types

Contact Block Types								
Contact		Single-pole Contact Block Type						
			/					
		1NO	1NC	1NO (early make)	1NC (late break)			
Туре	BST	BST010	BST001	BST010S	BST001S			
Push Rod		Green	Red	Black	White			

Note: BST contact blocks are not interchangeable with dark gray BS contact blocks used for ø30 control units.

Specifications, ratings, and mounting hole layouts are the same as ø30 control units. See "ø30 Series Control Units" on page 7.

Ordering Information

Standard Units


- Specify an operator or lens color code in the Type No.
- Black, green, and red colored buttons are included with flush pushbuttons.
- Full voltage type illuminated units are not supplied with a lamp. Order LED or incandescent lamps separately. Transformer type illuminated units contain an LED or incandescent lamp.
- Terminal covers, nameplates, and accessories are ordered separately.

Terminal Cover

• When a terminal cover is required, order an applicable terminal cover referring to page 55.

The Type No. development charts shown below can be used to specify control units other than those listed on the following


ø30 Series Diecast Zinc Pushbuttons



Note:


- Mushroom pull type AZD3 can have a maximum of two contact
- Mushroom push-pull type AYD31 can have a maximum of two contact blocks.

ø30 Series Diecast Zinc Pilot Lights




- Full voltage type is not supplied with a lamp.
- Transformer types contain an LED lamp (LSTD-6@ or LETD-6@) or incandescent lamp (LS-6, 1W or LE-8, 2W).
- LED lamps cannot be used on 480V AC transformers.
- Operating voltage codes 18, 118, 128, 28, 238, 248, 388, 48, and 488 are available for incandescent types only.

ø30 Series Diecast Zinc Illuminated **Pushbuttons**




- Illuminated pushbuttons cannot have an odd number of contact blocks, such as 1NO, 1NC, 3NO, 2NO-1NC, 1NO-2NC, and
- Full voltage type is not supplied with a lamp.
- Transformer types contain an LED lamp (LSTD-62) or LETD-62) or incandescent lamp (LS-6, 1W or LE-8, 2W).
- LED lamps cannot be used on 480V AC transformers.
- Operating voltage codes 18, 118, 128, 28, 238, 248, 388, 48, and 488 are available for incandescent types only.

ø30 Series Diecast Zinc Selector Switch




ø30 Series Diecast Zinc **Key Selector Switch**



Note:

• The key cannot be removed in the return position.

ø30 Series Diecast Zinc **Illuminated Selector Switch**



Note:

- Full voltage type is not supplied with a lamp.
- Transformer type contains an LED lamp (LSTD-62) or incandescent lamp (LS-6).
- LED lamps cannot be used on 480V AC transformers.

Flush / Extended / Extended with Half Shroud / Extended with Full Shroud

Type
Momentary Momentary 1NO-1NC ABD111N0 2NO ABD12N0 2NO-2NC ABD12N0 2NO-2NC ABD12N0 2NO-2NC ADD12N0 1NO-1NC ABD21N0 1NO-1NC ABD21N0 1NO-1NC ABD21N0 1NO-1NC ABD21N0 2NO ABD22N0 2NO-2NC ABD22N0 1NO-1NC ADD21N0 1NO-1NC
Momentary 2NO ABD120N① 2NC ABD102N① 2NO-2NC ABD122N① 1NO AOD110N① AOD110N① 1NC AOD111N① 2NO AOD120N① 2NO AOD120N① 2NO AOD120N① 2NO AOD122N① 2NO-2NC AOD122N① 2NO-2NC AOD122N① 2NO AOD122N① 2NO AOD122N① 2NO AOD122N① 2NO ADD122N① 2NO ADD122N① 2NO ABD20N① 2NO ABD20N① 1NO-1NC ABD211N① 1NO-1NC ABD211N① 2NO ABD22N① 2NO ABD2
ADD1 ADD12N① ABD12N① ABD12N① ABD12N① ADD12N① ADD11N① ADD11N① ADD11N① ADD11N① ADD11N① ADD11N① ADD11N① ADD11N① ADD11N② ADD12N① ADD12N① ADD12N① ADD12N① ADD12N① ADD12N① ADD12N② ADD12N③ ADD12N⑥ ADD12N
Company of the property of
Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button is required. Specify S, Y, or W when a blue, yellow, or white button
Specify S, Y, or W when a blue, yellow, or white button is required. 1NO ADD12N① 2NO AOD12N① 2NO-2NC AOD12N① 1NO-1NC ABD21N① 1NO-1NC ABD22N① 2NO ABD22N① 2NO ABD22N① 2NO-2NC A
Maintained Mainta
Maintained Mainta
2NO AOD120N① 2NC AOD102N① 2NO-2NC AOD122N① 2NO-2NC AOD122N① 1NO ABD210N① 1NO-1NC ABD211N① 2NO ABD220N① 2NO ABD220N① 2NO ABD220N① 2NO ABD222N① 2NO ABD222N① 2NO-2NC ABD222N① 2NO-2NC ABD222N① 2NO-2NC ABD222N① 1NC AOD21N① 1NO AOD210N① 1NO AOD210N① 1NO-1NC AOD211N①
C C Extended ABD2 Momentary ABD201N①
TNO ABD210N① 1NC ABD201N① 1NO-1NC ABD221N① 2NO ABD220N① 2NO-2NC ABD222N① 2NO-2NC ABD222N① 2NO-2NC ABD222N① 1NO AOD21N① 1NO-1NC AOD21N① 1NO-1NC AOD201N① 1NO-1NC AOD201N① 1NO-1NC AOD201N① 1NO-1NC AOD201N① 1NO-1NC AOD201N① 1A.5 Terminal Screw Panel Thickness 0.8 to 7.5 23 24 24 25 25 23 24 25 25 25 25 25 25 25
ABD2 Momentary
Momentary
Momentary 2NO ABD220N① 2NC ABD202N① 2NO-2NC ABD222N① Extended AOD2 1NC AOD201N① 1NO-1NC AOD201N① 1NO-1NC AOD211N①
2NC ABD202N① 2NO-2NC ABD222N① Extended AOD2 1NO AOD21N① 1NO-1NC AOD211N① 1NO-1NC AOD211N①
Extended AOD2 Maintained AOD2 ADD21N① 1NO AOD21N① 1NO-1NC AOD211N① 1NO-1NC AOD211N①
Extended AOD2 1NO AOD210N① 1NC AOD201N① 1NO-1NC AOD211N① 1NO-1NC AOD211N① 76 (3 or 4 blocks)
AOD2 1NC AOD201N① 1NO-1NC AOD211N① 1NO-1NC AOD211N① 76 (3 or 4 blocks) 14.5
Maintained 1NO-1NC AOD211N① 14.5 76 (3 or 4 blocks)
Maintained (3 of 4 blocks)
2NC AOD202N®
(h) (h) (1 € 2NO-2NC AOD222N①
Extended with Half Shroud 1NO ABGD210N①
ABGD2 1NC ABGD201N①
1NO-1NC ABGD211N① Specify a button
Nomentary 2NO ABGD220N① color code in M3.5 Terminal Screw JL Panel Thickness 0.8 to 3.5
2NC ABGD202N® place of ① in the Type No.
⊕ ⊕ C € 2NO-2NC ABGD222N⊕ B: black
Extended with Half Shroud 1NO AOGD210N① G: green
AOGD2 1NC AOGD201N① R: red S: blue R: red S: blue
Maintained 1NO-1NC AOGD211N① W: white 72.5 (3 or 4 blocks)
2NO AOGD220N① Y: yellow
2NC AOGD202N①
2NO-2NC AOGD222N①
Extended with Full Shroud ABFD2 ABFD201N©
INC ABPD201NU
Momentary 1NO-1NC ABFD211N① 2NO ABFD220N① M3.5 Terminal Screw Panel Thickness 0.8 to 6
2NO ABFD220N① 2NC ABFD202N① ABFD202N① AM3.5 Terminal Screw Panel Thickness 0.8 to 6
© © C € 2NO-2NC ABFD222N①
Extended with Full Shroud 1NO AOFD210N®
AOFD2 1NC AOFD201N①
1NO-1NC AOFD211N① 74.5 (3 or 4 blocks)
Maintained 2NO AOFD220N®
2NC AOFD202N①
<u>₩</u> ∰ (€ 2NO-2NC AOFD222N①

- Round bezel and shroud (metal): Chrome-plated
- Pushbuttons with one or three contact blocks contain a dummy block
- Other contact arrangements are also available. See page 67.

Mushroom / Jumbo Mushroom Types

Shape	Operation Type	Contact	Type No.	① Button Color Code	Dimensions (mm)
Mushroom		1NO	ABD310N®		
ABD3		1NC	ABD301N®		
-	Managara	1NO-1NC	ABD311N®		
	Momentary	2NO	ABD320N®		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
		2NC	ABD302N®		
(1) (1) (1) (1) (1) (1) (1) (1) (1) (1)		2NO-2NC	ABD322N®		
Mushroom		1NO	AOD310N®		5.5 23 40
AOD3		1NC	AOD301N®		53 (1 or 2 blocks)
	Maintained	1NO-1NC	AOD311N ^①		76 (3 or 4 blocks) 22
	Maintained	2NO	AOD320N®		
		2NC	AOD302N®	B: black	
(1) (1) (1) (1) (1) (1) (1) (1) (1) (1)		2NO-2NC	AOD322N①	G: green	
Mushroom with Full Shroud		1NO	ABGD310N®	R: red W: white	
ABGD3		1NC	ABGD301N®	Y: yellow	
		1NO-1NC	ABGD311N①		
	Momentary	2NO	ABGD320N®		M3.5 Terminal Screw Panel Thickness 0.8 to 6.5
		2NC	ABGD302N①		
		2NO-2NC	ABGD322N①		
Mushroom with Full Shroud	Maintained	1NO	AOGD310N①		5.5 23
AOGD3		1NC	AOGD301N①		52 (1 or 2 blocks) 23
		1NO-1NC	AOGD311N①		75 (3 or 4 blocks)
		2NO	AOGD320N®		
		2NC	AOGD302N①		
		2NO-2NC	AOGD322N①		
Jumbo Mushroom		1NO	ABD410N®		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
ABD4		1NC	ABD401N®		
	Managara	1NO-1NC	ABD411N®		
4	Momentary	2NO	ABD420N®		5.5 23
		2NC	ABD402N®		53 (1 or 29 blocks) 29
(l) (g) (€		2NO-2NC	ABD422N①		76 (3 or 4 blocks)
Jumbo Mushroom with		1NO	ABGD410N®		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
Shallow Shroud ABGD4		1NC	ABGD401N®	B: black DG: dark green	
	Managara	1NO-1NC	ABGD411N①	DR: dark green	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0
	Momentary	2NO	ABGD420N®	G: green	5.5 23
		2NC	ABGD402N®	R: red Y: yellow	53 (1 or 2 blocks) 29
LISTED (F)		2NO-2NC	ABGD422N①	, ,	76 (3 or 4 blocks)
Jumbo Mushroom with		1NO	ABFD410N ^①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
Deep Shroud ABFD4		1NC	ABFD401N①		
ADI D4	Mamaratar	1NO-1NC	ABFD411N①		
	Momentary	2NO	ABFD420N①		5.5 23
		2NC	ABFD402N①		53 (1 or 2 blocks) 32.5
UL STED SP. (E		2NO-2NC	ABFD422N①		76 (3 or 4 blocks)

- \bullet Specify a button color code in place of $\ensuremath{\textcircled{1}}$ in the Type No.
- Round bezel and shroud (metal): Chrome-plated
- Pushbuttons with one or three contact blocks contain a dummy block
- Other contact arrangements are also available. See page 67.

Pushlock Turn Reset / Push Turn Lock / Pull / Push-Pull / Pin Lock Types

Shape	Contact	Type No.	① Button Color Code	Dimensions (mm)
Mushroom Pushlock Turn Reset	1NO	AVD310N①		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
AVD3	1NC	AVD301N①		
E (1NO-1NC	AVD311N①	R: red	
4.	2NO	AVD320N①	Y: yellow	5.5 23
	2NC	AVD302N①		53 (1 or 2 blocks) 24
	2NO-2NC	AVD322N①		76 (3 or 4 blocks)
Mushroom Push Turn Lock	1NO	AJD310N®		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
AJD3	1NC	AJD301N ^①	B: black	
	1NO-1NC	AJD311N①	G: green	
33 4	2NO	AJD320N®	R: red	5.5 23 40
0000	2NC	AJD302N①	Y: yellow	53 (1 or 2 blocks) 24
	2NO-2NC	AJD322N①		76 (3 or 4 blocks)
Mushroom Pull AZD3	1NO	AZN310N®		
	1NO-1NC	AZN311N①		
	2NO	AZN320N®		M3.5 Terminal Screw Panel Thickness 0.8 to 7.5
United ()	2NC	AZN302N®		
Mushroom Push-Pull AYD31	1NO-1NC	AYD3111N①	B: black	5.5 23
	2NO	AYD3120N①	G: green R: red S: blue	53 (1 or 2 blocks) 30.5
U) USTED SP	2NC	AYD3102N①	Y: yellow	
Pin Lock	1NO	ABD8P10N①		Panel Thickness
ABD8P	1NC	ABD8P01N①		M3.5 Terminal Screw
	1NO-1NC	ABD8P11N①		252 000 000 253
	2NO	ABD8P20N①		5.5, 23
	2NC	ABD8P02N①		53 (1 or 40
(I) (I) (E) (E) (I) (I) (I) (I) (I) (I) (I) (I) (I) (I	2NO-2NC	ABD8P22N①		2 blocks) 28.5 76 (3 or 4 blocks)

- Specify a button color code in place of ① in the Type No.
- Round bezel (metal): Chrome-plated
- Pushbuttons with one or three contact blocks contain a dummy
- Other contact arrangements are also available. See page 67.
- Pushlock Turn Reset: Button is maintained when pressed and is reset when turned clockwise. Red buttons only.

Note: AVD3 pushlock turn reset switches cannot be used as emergency stop switches. When emergency stop switches are required, use the HN1E series emergency stop switches (ISO 13850 and IEC 60947-5-5 compliant).

- Push Turn Lock: Button is locked when turned clockwise in the depressed position and is reset when turned counterclockwise.
- Pull: Pulling the button operates the contacts. Up to 2 contact blocks (1 layer) can be mounted on pull switches.
- Push-Pull: Button is maintained in both depressed and reset positions. Up to 2 contact blocks (1 layer) can be mounted on AYD31 push-pull switches.
- Pin Lock: Button can be locked in either depressed or reset position by inserting the pin. Pad lock with a ø5mm pin can also be used to lock the button.

Contact Operation

Pull Switch (Spring Return)

		,		
Contact	AZD3			
Contact	Normal	Pull		
1NO	9,0	- -		
1NC	•	•1•		
1NO-1NC	ის •1•	<u></u>		
2NO	0 ¹ 0 0 ¹ 0	~ · · ·		
2NC	<u> </u>	●1● ●1●		

Push-Pull Switch (Maintained)

Contact	AYD31				
Contact	Push	Pull			
1NO-1NC	<u>0,0</u>	~ • • • • • • • • • • • • • • • • • • •			
2NO	9-0 9-0	 			
2NC	•.• •.•	316 316			

Note: Pull and push-pull switches can have a maximum of two contact blocks.

ø30 ø30 Diecast Zinc Series Pilot Lights

Dome Types

Shape	Lamp	Input Type	Lamp Receptacle	Type No.	② Lens/LED Color Code	Applicable Lamp
Dome APD1 APDE1	PD1	Full Voltage	BA9S	APD199N@	A: amber C: clear G: green R: red	LSTD LS (1W)
			E12	APDE199N@	S: blue W: white Y: yellow	LETD LE (2W)
	150	Total	BA9S	APD13DN2	A: amber G: green PW: pure white (BA9S only)	LSTD-6@
(I)	LED	Transformer	E12	APDE13DN2	R: red S: blue W: white Y: yellow	LETD-6@
	Incandescent	Transformer	BA9S	APD13N2	A: amber C: clear G: green	LS-6 (1W)
(h) (f) (f	andoson	Hansiormer	E12	APD13N2	R: red S: blue W: white	LE-8 (2W)

• Operating Voltage Code


Specify an operating voltage code in place of ③ in the Type No.

③ Operating Voltage Code	
LED Transformer BA9S and E12 Types Incandescent Transformer BA9S Type	Incandescent Transformer E12 Type
16: 100/110V AC	18: 100/110V AC
116: 115V AC	118: 115V AC
126: 120V AC	128: 120V AC
26: 200/220V AC	28: 200/220V AC
236: 230V AC	238: 230V AC
246: 240V AC	248: 240V AC
386: 380V AC	388: 380V AC
46: 400/440V AC	48: 400/440V AC
486: 480V AC (incandescent only)	488: 480V AC


- Specify a lens/LED color code in place of ② in the Type No. Use the white lens (W) for LED pure white illumination.
- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer and DC-DC converter types contain an LED lamp: LSTD-6@ or LETD-6@ (rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp: LS-6 (1W, 6V AC/DC) or LE-8 (2W, 18V AC/DC).

Dimensions

• Full Voltage Type



• Transformer Type



All dimensions in mm.

Round Extended Illuminated Pushbuttons

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALD29911N2	
ALD2			Without Lamp	Full Voltage	2NO	ALD29920N2	LSTD LS (1W)
AOLD2					2NC	ALD29902N2	
				Transformer	1NO-1NC	ALD2311DN2	
		Momentary	LED		2NO	ALD2320DN2	LSTD-6@
					2NC	ALD2302DN2	1
			Incandescent	Transformer	1NO-1NC	ALD2311N2	LS-6
31					2NO	ALD2320N2	
	BA9S				2NC	ALD2302N2	
(I)	BA95		Without Lamp	Full Voltage	1NO-1NC	AOLD29911N2	LSTD LS (1W)
					2NO	AOLD29920N2	
The same of the sa					2NC	AOLD29902N2	
Din					1NO-1NC	AOLD2311DN2	
		Maintained	LED	Transformer	2NO	AOLD2320DN2	LSTD-62
					2NC	AOLD2302DN2	1
			Incandescent		1NO-1NC	AOLD2311N2	LS-6
				Transformer	2NO	AOLD2320N2	
					2NC	AOLD2302N2	


Color Code and Operating Voltage Code

② Lens/LED Color Code	② Lens Color Code	③ Operating Voltage Code		
LED Illuminated Type	Incandescent Illuminated Type	S Operating voltage code		
Specify a lens/LED color code in place of ② in the Type No.	Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.		
A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Use the white lens (W) for LED pure white illumination.	A: amber C: clear G: green R: red S: blue W: white	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC (incandescent only)		


- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp (LSTD-62, rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp (LS-6, rated voltage 6V AC/DC, 1W).

Dimensions

ALD2/AOLD2 Full Voltage



• ALD2/AOLD2 BA9S/Transformer



ø30 Ø30 Diecast Zinc Series Illuminated Pushbuttons

Round Extended with Full Shroud Illuminated Pushbuttons

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Round Extended					1NO-1NC	ALFD29911N2	LOTE
with Full Shroud			Without Lamp	Full Voltage	2NO	ALFD29920N2	LSTD LS (1W)
ALFD2 AOLFD2					2NC	ALFD29902N2	[[[[]
AOLI DZ			LED	Transformer	1NO-1NC	ALFD2311DN2	
3		Momentary			2NO	ALFD2320DN2	LSTD-62
18					2NC	ALFD2302DN2	1
8			Incandescent	Transformer	1NO-1NC	ALFD2311N2	LS-6
					2NO	ALFD2320N2	
	BA9S				2NC	ALFD2302N2	
⊕ €	BA93			Full Voltage	1NO-1NC	AOLFD29911N2	LSTD LS (1W)
USTED			Without Lamp		2NO	AOLFD29920N®	
					2NC	AOLFD29902N2	
3					1NO-1NC	AOLFD2311DN2	
		Maintained	LED	Transformer	2NO	AOLFD2320DN2	LSTD-62
					2NC	AOLFD2302DN2	1
			Incandescent		1NO-1NC	AOLFD2311N2	LS-6
0.611				Transformer	2NO	AOLFD2320N2	
					2NC	AOLFD2302N2	


Color Code and Operating Voltage Code

② Lens/LED Color Code	② Lens Color Code	③ Operating Voltage Code		
LED Illuminated Type	Incandescent Illuminated Type	Soperating voltage code		
Specify a lens/LED color code in place of ② in the Type No.	Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.		
A: amber G: green PW: pure white R: red S: blue W: white Y: yellow Use the white lens (W) for LED pure white	A: amber C: clear G: green R: red S: blue W: white	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC (incandescent only)		


- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp (LSTD-62), rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp (LS-6, rated voltage 6V AC/DC, 1W)

Dimensions

• ALFD2/AOLFD2 Full Voltage



ALFD2/AOLFD2 Transformer



Mushroom (ø40) Illuminated Pushbuttons

Shape	Lamp Receptacle	Operation Type	Lamp	Input Type	Contact	Type No.	Applicable Lamp
ø40 Mushroom					1NO-1NC	ALD39911DN2	
ALD3	BA9S	Mamantani	Without Lamp	Full Voltage	2NO	ALD39920DN2	LSTD
AOLD3					2NC	ALD39902DN2	1
		Momentary	LED	Transformer	1NO-1NC	ALD3@11DN@	LSTD-62
					2NO	ALD3@20DN@	
					2NC	ALD3@02DN@	
					1NO-1NC	AOLD39911DN2	LSTD
3			Without Lamp	Full Voltage	2NO	AOLD39920DN2	
		Maintained			2NC	AOLD39902DN2	
⊕ (€		Maintained			1NO-1NC	AOLD3311DN2	LSTD-6@
			LED	Transformer	2NO	AOLD3320DN2	
					2NC	AOLD3@02DN@	


Color Code and Operating Voltage Code

② Lens/LED Color Code	③ Operating Voltage Code						
LED Illuminated Type	LED Transformer BA9S Type Specify an operating voltage code in place of ③ in the Type No.						
Specify a lens/LED color code in place of ② in the Type No.							
A: amber G: green R: red W: white Y: yellow	16: 100/110V AC 116: 115V AC 126: 120V AC 26: 200/220V AC 236: 230V AC 246: 240V AC 386: 380V AC 46: 400/440V AC						


- Full voltage types do not contain a lamp. Order LED lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp (LSTD-6@, rated voltage 6V AC/DC).

Dimensions

 ALD3/AOLD3 Full Voltage



 ALD3/AOLD3 Transformer



ø30 ø30 Diecast Zinc Series Illuminated Pushbuttons

Mushroom Pushlock Turn Reset Types

Shape	Lamp Receptacle	Lamp	Input Type	Contact	Type No.	Applicable Lamp
Mushroom Pushlock Turn				1NO-1NC	AVLD39911NR	LOTE
Reset AVLD3		Without Lamp	Full Voltage	2NO	AVLD39920NR	LSTD LS (1W)
AVLD3 AVLDE3				2NC	AVLD39902NR	
-				1NO-1NC	AVLD3@11DNR	
	BA9S	LED	Transformer	2NO	AVLD3@20DNR	LSTD-62
				2NC	AVLD3@02DNR	1
				1NO-1NC	AVLD3@11NR	
		Incandescent	Transformer	2NO	AVLD3@20NR	LS-6
				2NC	AVLD3@02NR	
			Full Voltage	1NO-1NC	AVLDE39911NR	LETD LE (2W)
		Without Lamp		2NO	AVLDE39920NR	
				2NC	AVLDE39902NR	
				1NO-1NC	AVLDE3@11DNR	
	E12	LED	Transformer	2NO	AVLDE3@20DNR	LETD-62
				2NC	AVLDE3@02DNR	
				1NO-1NC	AVLD3@11NR	
Lister		Incandescent	Transformer	2NO	AVLD3@20NR	LE-8
				2NC	AVLD3@02NR	


Operating Voltage Code

③ Operating Voltage Code									
LED Transformer BA9S and E12 Types Incandescent Transformer BA9S Type	Incandescent Transformer E12 Ty								
16: 100/110V AC	18: 100/110V AC								
116: 115V AC	118: 115V AC								
126: 120V AC	128: 120V AC								
26: 200/220V AC	28: 200/220V AC								
236: 230V AC	238: 230V AC								
246: 240V AC	248: 240V AC								
386: 380V AC	388: 380V AC								
46: 400/440V AC	48: 400/440V AC								
486: 480V AC (incandescent only)	488: 480V AC								


- Color code: R (red)
- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp (LSTD-62), rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp (LS-6, rated voltage 6V AC/DC, 1W)
- Pushlock Turn Reset: Lens is maintained when pressed and is reset when turned clockwise. Red lens only.
- Note: AVLD3 and AVLDE3 pushlock turn reset switches cannot be used as emergency stop switches. When emergency stop switches are required, use the HN1E series emergency stop switches (ISO 13850 and IEC 60947-5-5 compliant).

Dimensions


 AVLD3 BA9S/Full Voltage




• AVLDE3 E12/Full Voltage



BA9S/Transformer



• AVLD3/AVLDE3 E12/Transformer







ASD Selector Switches (Knob Operator Type)

SI	Shape						ASD				
No. of Positions	Co	ntact Arra	angem	ent C	hart		♠ ♠ (€				
	Contact	Contact	Block	Oper	ator Po	sition	Maintained	Spring Return from Right	Spring Return from Left		
	Code (ASD)	Mounting Position	ting ion Type L R			LR	LR	LR			
sitio	10 (1NO)	1 2	NO Dummy		•		ASD210N	ASD2110N	ASD2210N *		
90° 2-position	11 (1NO-1NC)	1 2	NO NC	•	•		ASD211N	ASD2111N	ASD2211N *		
06	20 (2NO)	1 2	NO NO		•		ASD220N	ASD2120N	ASD2220N *	_	
	22 (2NO-2NC)	1 2 3 4	NO NC NO	•	•		ASD222N	ASD2122N	ASD2222N *		
	Contact	Contact	Block	Block Operator Position			Maintained	Spring Return from Right	Spring Return from Left	Spring Return Two-way	
	Code (ASD)	Mounting Position	Type	L	L C R		L C R	L C R	L_ R	L C R	
	20 (2NO)	1 2	NO NO	•		•	ASD320N	ASD3120N	ASD3220N	ASD3320N	
3-position	40 (4NO)	1 2 3 4	NO NO NO	•		•	ASD340N	ASD3140N	ASD3240N	ASD3340N	
45° 3	22 (2NO-2NC)	1 2 3 4	NO NO NC	•			- ASD322N	ASD3122N	ASD3222N	ASD3322N	
	02 (2NC)	1 2	NC NC				ASD302N	ASD3102N	ASD3202N	ASD3302N	
	04 (4NC)	1 2 3 4	NC NC NC				ASD304N	ASD3104N	ASD3204N	ASD3304N	


- Knob: Black
- Round bezel (metal): Chrome-plated
- Selector switches with one contact block contain a dummy block.
- On the 2-position selector switches marked with * above, the contact operation is reversed as follows.



• Contact Block Mounting Position and **Contact Arrangement Chart**




Dimensions



ASD Selector Switches (Lever Operator Type)


No. of Positions	Shape						ASD*L				
_	Contact	Contact		Operator Position			Maintained	Spring Return from Right	Spring Return from Left		
	Code (ASD)	Mounting Position	Туре	L	R		LR	LR	L_W_R		
sition	10 (1NO)	1 2	NO Dummy		•		ASD2L10N	ASD21L10N	ASD22L10N *		
2-position	11 (1NO-1NC)	1 2	NO NC	•	•		ASD2L11N	ASD21L11N	ASD22L11N *		
06	20 (2NO)	1 2	NO NO		•		ASD2L20N	ASD21L20N	ASD22L20N *	_	
	22 (2NO-2NC)	1 2 3 4	NO NC NO	•	•		ASD2L22N	ASD21L22N	ASD22L22N *		
	Contact	Contact		Operator Position			Maintained	Spring Return from Right	Spring Return from Left	Spring Return Two-way	
	Code (ASD)	Mounting Position	Туре	L	С	R	L C R	L C R	L_ R	L_C_R	
	20 (2NO)	1 2	NO NO	•		•	ASD3L20N	ASD31L20N	ASD32L20N	ASD33L20N	
3-position	40 (4NO)	1 2 3 4	NO NO NO	•		•	ASD3L40N	ASD31L40N	ASD32L40N	ASD33L40N	
45° 3-	22 (2NO-2NC)	1 2 3 4	NO NO NC NC	•		•	ASD3L22N	ASD31L22N	ASD32L22N	ASD33L22N	
	02 (2NC)	1 2	NC NC				ASD3L02N	ASD31L02N	ASD32L02N	ASD33L02N	
	04 (4NC)	1 2 3 4	NC NC NC				ASD3L04N	ASD31L04N	ASD32L04N	ASD33L04N	

- Lever: Black
- Round bezel (metal): Chrome-plated
- Selector switches with one contact block contain a dummy block.
- On the 2-position selector switches marked with * above, the contact operation is reversed as follows.




• Contact Block Mounting Position and **Contact Arrangement Chart**





Dimensions



ASD Key Selector Switches


No. of Positions	Shape Cor	ntact Arra	angem	ent C	hart		ASD*K				
	Contact	Contact Block Operator Position					Maintained	Spring Return from Right	Spring Return from Left		
ے	Code (ASD)	Mounting Position	Туре	L	R		LR	LR	LR		
sitio	10 (1NO)	1 2	NO Dummy		•		ASD2K10N	ASD21K10N	ASD22K10N *		
90° 2-position	11 (1NO-1NC)	1 2	NO NC	•	•		ASD2K11N	ASD21K11N	ASD22K11N *		
06	20 (2NO)	1 2	NO NO		•		ASD2K20N	ASD21K20N	ASD22K20N *] -	
	22 (2NO-2NC)	1 2 3 4	NO NC NO	•	•		ASD2K22N	ASD21K22N	ASD22K22N *		
	Contact	Contact	Contact Block				Maintained	Spring Return from Right	Spring Return from Left	Spring Return Two-way	
	Code (ASD)	Mounting Position	Туре	L	С	R	L C R	L C R	L_ R	L_C_R	
	20 (2NO)	1 2	NO NO	•		•	ASD3K20N	ASD31K20N	ASD32K20N	ASD33K20N	
3-position	40 (4NO)	1 2 3 4	NO NO NO	•		•	- ASD3K40N	ASD31K40N	ASD32K40N	ASD33K40N	
45° 3	22 (2NO-2NC)	1 2 3 4	NO NO NC NC	•		•	ASD3K22N	ASD31K22N	ASD32K22N	ASD33K22N	
	02 (2NC)	1 2	NC NC				ASD3K02N	ASD31K02N	ASD32K02N	ASD33K02N	
	04 (4NC)	1 2 3 4	NC NC NC				- ASD3K04N	ASD31K04N	ASD32K04N	ASD33K04N	

- Cylinder: Black
- Round bezel (metal): Chrome-plated
- On the spring-returned types, the keys can be released only from the maintained positions. On the maintained types, the key can be released from every position. Key retained positions are also available. See page 12.
- Key selector switches are supplied with two standard keys.
- Key selector switches with one contact block contain a dummy block.
- On the 2-position selector switches marked with * above, the contact operation is reversed as follows.


[Example]

• Contact Block Mounting Position and **Contact Arrangement Chart**





• Dimensions



ø30 ø30 Diecast Zinc Series Illuminated Selector Pushbuttons

Illuminated Selector Switches


90° 2-position

Shape					ASLD (Base BA98	S)				
Conta	ct Arranç	gemer	nt Cha	nrt						
Contact Code	Contact Oper Block Posi				Lamp	Input Type	Maintained	Spring Return from Right	Spring Return from Left	
Code	Mounting Position	Туре	L	R		, ,,	L		, r	
	1	NO		•	Without Lamp	Full Voltage	ASLD29911N2	ASLD219911N2	ASLD229911N2 *	
11 (1NO-1NC)	2	NC	•		LED	Transformer	ASLD2311DN2	ASLD21311DN2	ASLD22311DN2 *	
					Incandescent	Transformer	ASLD2311N2	ASLD21311N2	ASLD22311N2 *	
	1	NO		•	Without Lamp	Full Voltage	ASLD29920N2	ASLD219920N@	ASLD229920N② *	
20 (2NO)	2	NO		•	LED	Transformer	ASLD2320DN2	ASLD21320DN2	ASLD22320DN2 *	
					Incandescent	Transformer	ASLD2320N2	ASLD21320N2	ASLD22320N2 *	
	1	NO		•	Without Lamp	Full Voltage	ASLD29922N2	ASLD219922N2	ASLD229922N② *	
	2	NC	•		Without Lamp	1 un voltage	AOLD 2392 ZING	AOLDZ I JOZZING	AGEDZZJ9ZZING **	
22 (2NO-2NC)	3	NO		•	LED	Transformer	ASLD2322DN2	ASLD21322DN2	ASLD22322DN2 *	
(ZINO-ZINO)	4	NC	•							
					Incandescent	Transformer	ASLD2322N2	ASLD21322N2	ASLD22322N2 *	

Color Code and Operating Voltage Code


* Color Code and Operating voi	9				
LED Illuminated Type	Incandescent Illuminated Type	③ Operating Voltage Code			
② Lens/LED Color Code	② Lens Color Code				
Specify a lens/LED color code in place of ② in the Type No. A: amber G: green R: red S: blue W: white Y: yellow	Specify a lens color code in place of ② in the Type No. A: amber G: green R: red S: blue W: white	Specify an operating voltage code in place of ③ in the Type No. 16: 100/110V AC 156: 115V AC 136: 120V AC 26: 200/220V AC 236: 230V AC 256: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC (incandescent only)			

- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp (LSTD-62), rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp (LS-6, rated voltage 6V AC/DC).
- On the 2-position selector switches marked with * above, the contact operation is reversed as follows.




Contact Block Mounting Position and Contact Arrangement Chart





Dimensions



Illuminated Selector Switches

45° 3-position

Contact	Contact Block		Operator Position			Lamp	Maintained	Spring Return from Right	Spring Return from left	Spring Return Two-way	
Code	Mounting Position	Туре	Type L C R		R	Input Type	L R	L R	LR	L R	
	1	NO	•			Without Lamp Full Voltage	ASLD39920N2	ASLD319920N2	ASLD329920N2	ASLD339920N2	
20 (2NO)	2	NO			•	LED Transformer	ASLD3320DN2	ASLD31320DN2	ASLD32320DN2	ASLD33320DN2	
						Incandescent Transformer	ASLD3320N2	ASLD31320N2	ASLD32320N2	ASLD33320N2	
	1	NC		-		Without Lamp Full Voltage	ASLD39902N2	ASLD319902N@	ASLD329902N2	ASLD339902N2	
02 (2NC)	2	NC	_			LED Transformer	ASLD3302DN2	ASLD31302DN2	ASLD32302DN2	ASLD33@02DN@	
						Incandescent Transformer	ASLD3302N2	ASLD31302N2	ASLD32302N2	ASLD33302N2	
22 (2NO-2NC)	2	NO NO	•		•	Without Lamp Full Voltage	ASLD39922N2	ASLD319922N@	ASLD329922N2	ASLD339922N2	
	3	NC NC		5		LED Transformer	ASLD3322DN2	ASLD31322DN2	ASLD32322DN2	ASLD33322DN2	
	-	110				Incandescent Transformer	ASLD3322N2	ASLD31322N2	ASLD32322N2	ASLD33322N2	
	1 2	NO NO	•		•	Without Lamp Full Voltage	ASLD39940N2	ASLD319940N2	ASLD329940N@	ASLD339940N2	
40 (4NO)	3 4	NO NO	•		•	LED Transformer	ASLD3@40DN@	ASLD31340DN2	ASLD32340DN2	ASLD33340DN2	
						Incandescent Transformer	ASLD3@40N@	ASLD31340N2	ASLD32340N2	ASLD33340N2	
04 (4NC)	1 2	NC NC				Without Lamp Full Voltage	ASLD39904N2	ASLD319904N2	ASLD329904N2	ASLD339904N2	
	3 4	NC NC				LED Transformer	ASLD3304DN2	ASLD31304DN2	ASLD32304DN2	ASLD33304DN2	
						Incandescent Transformer	ASLD3304N2	ASLD31304N2	ASLD32304N2	ASLD33304N2	


Color Code and Operating Voltage Code

LED Illuminated Type	Incandescent Illuminated Type	3 Operating Voltage Code				
② Lens/LED Color Code	② Lens Color Code	© Operating voltage Code				
Specify a lens/LED color code in place of ② in the Type No.	Specify a lens color code in place of ② in the Type No.	Specify an operating voltage code in place of ③ in the Type No.				
A: amber G: green R: red S: blue W: white Y: yellow	A: amber G: green R: red S: blue W: white	16: 100/110V AC 156: 115V AC 136: 120V AC 26: 200/220V AC 236: 230V AC 256: 240V AC 386: 380V AC 46: 400/440V AC 486: 480V AC (incandescent only)				


- Full voltage types do not contain a lamp. Order LED or incandescent lamps separately. For lamps, see page 63.
- LED illuminated transformer types contain an LED lamp (LSTD-6@, rated voltage 6V AC/DC).
- Incandescent illuminated transformer types contain an incandescent lamp (LS-6, rated voltage 6V AC/DC).

• Contact Block Mounting Position and Contact Arrangement Chart





• Dimensions



Ring Operator Type / Lever Operator Type Selector Pushbuttons

						Ring	Lever				
Shape	Contact	Circuit	Conta		F			•	Ring Operator	Lever Operator	Color
Snapo	Code	Code									
					Pushbutton		Type No.	Type No.			
			Mounting Position	Туре	Normal	Push	Normal	Push	туре но.	.,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	
Ring Operator		A03	1	NO		•		•	ASBD211N-A03①	ASBD2L11N-A03①	
(90° 2-Position) ASBD2	11 (1NO-1NC)		2	NC	•						
	(INO-INC)	G03	2	NO NC		•		Blocked	ASBD211N-G03①	ASBD2L11N-G03①	
200			1	NO	•	•	•	•			B: black G: green R: red Y: yellow
			2	NC	•						
		A08	3	NO		•		•	ASBD222N-A08®	ASBD2L22N-A08®	
			4	NC	•						
			1	NO		•		•	ASBD222N-C10① - ASBD222N-D10①	ASBD2L22N-C10① ASBD2L22N-D10①	
		C10	2	NO				•			
			3	NC	•						
<u>⊕</u> ⊕ (€			4	NC							
			1	NO		•					
Lever Operator (90° 2-Position)		D10	3	NO NC	_			•			
ASBD2L			4	NC	•						
	22 (2NO-2NC)		1	NO		-					
1			2	NO				•			
		E10	3	NC					ASBD222N-E10①	ASBD2L22N-E10①	
			4	NC							
			1	NO				•			
		F10	2	NO		•			ASBD222N-F10①	ASBD2L22N-F10①	
68		1.10	3	NC			•		NOBBELLENT 10®	NODDZEZZIVI 100	
~			4	NC	•						
			1	NO		•			ASBD222N-G10①	ASBD2L22N-G10①	
		G10	3	NO NC	•	•		Blocked			
(I)			4	NC	•		•				
			-	INC							

- Specify a button color code in place of ① in the Type No.
- Ring/Lever (Metal): Chrome-plated

- 1. Circuit Code G: The pushbutton does not operate when the ring or lever operator is turned to the right position.
- 2. Circuit Codes E and F: The right and left NC contact blocks on circuit code E or F may overlap each other while turning the ring or lever operator. The NO and NC contact blocks on circuit code F may overlap each other while pressing the button.
- 3. When using the selector pushbutton, do not turn the ring or lever operator with the pushbutton depressed. Otherwise, damage or failure may be caused.
- 4. When installing the lever operator, make sure that the lever is not in the horizontal position. Otherwise, shock resistance may be degraded.


Contact Block Mounting Position and Contact Arrangement Chart




	Normal	Push
1		•
2	•	
3		•
4	•	

Dimensions

Ring Operator (90° 2-position) ASBD2



Lever Operator (90° 2-position) ASBD2L



Accessories (For Diecast Zinc Series Only)

For other accessories, see pages 55 to 63.

Shape	Material	Type No.	Ordering Type No.	Package Quantity	Description
Metal Bezel	OG-81 OG-81PN02 2 Chrome-plated		2	Cannot be used with half-shrouds.	
Flush Extended (Octagonal)	Ciliome-plated	OG-82	OG-82	1	Calliot be used with Hall-Sillouds.
Spare Key	Metal	TW-SK-0	TW-SK-0PN02	2	For key selector switches

Maintenance Parts (For Diecast Zinc Series Only)

Shape	Specificati	on	Type No.	Ordering Type No.	Package Quantity	Description
Button		0	ABN1BN-①	ABN1BN-①PN05	5	Specify a color code in place of ①. B (black), G (green), R (red), S
	Plastic	0	ABN2BN-①	ABN2BN-①PN05	5	(blue), W (white), Y (yellow) • Above colors are used for Ø30
• Flush • Extended		0	ABN3BN-①	ABN3BN-①PN02	2	diecast zinc control units (light colored operator units).
Dummy Block	Plastic		BST-D	BST-DPN10	10	Used for 1NO or 1NC contact blocks. Snaps on to the operator unit.
Selector Operator •Knob •Lever	Plastic	0	ASNHT-①	ASNHT-①PN02	2	Specify a color code in place of ①.
	Tiastic	0	ASNHL-①	ASNHL-①PN02	2	B (blue), G (green), R (red)
❸ Color Insert	Color Insert	•	TW-HC1①	TW-HC1①PN05	5	Specify a color code in place of ①. B (black), G (green), R (red), S (blue), W (white), Y (yellow)

Safety Precautions

- Turn off the power to the ø30 diecast zinc control units before starting installation, removal, wiring, maintenance, and starting installation, removing, wiring, maintenance, and inspection of the products. Failure to turn power off may cause electrical shocks or fire hazard.
- To avoid a burn on your hand, use the lamp holder tool when replacing lamps.
- For wiring, use wires of a proper size to meet the voltage and current requirements. Tighten the M3.5 terminal screws to a tightening torque of 1.0 to 1.3 N·m. Failure to tighten terminal screws may cause overheat and fire.

Instructions

Tightening Torque for Terminal Screws

Tighten the M3.5 terminal screws to a torque of 1.0 to 1.3 N·m.

Replacement of Lamps

Lamps can be replaced by using the lamp holder tool (OR-55) from the front of the panel.

• How to remove

To remove, slip the lamp holder tool onto the lamp head lightly. Then push slightly, and turn the lamp holder tool counterclockwise.

How to install

To install, insert the lamp head into the lamp holder tool. Place the pins on the lamp base to the grooves in the lamp socket. Inset the lamp and turn it clockwise.

Installation of LED Illuminated Units

• When using full voltage type LED illuminated units, provide protection against electrical noise, if necessary. See page 65 for notes on LED illuminated units.





Specifications and other descriptions in this catalog are subject to change without notice.



IDEC IZUMI CORPORATION

7-31, Nishi-Miyahara 1-Chome, Yodogawa-ku, Osaka 532-8550, Japan Tel: +81-6-6398-2571, Fax: +81-6-6392-9731 www.idec.com

IDEC CORPORATION (USA)

1175 Elko Drive, Sunnyvale, CA 94089-2209, USA Tel: +1-408-747-0550, Toll Free: (800) 262-IDEC, Fax: +1-408-744-9055

E-mail: opencontact@idec.com, www.idec.com

IDEC CANADA LIMITED

Unit 22-151, Brunel Road Mississauga, Ontario, L4Z 1X3, Canada Tel: +1-905-890-8561, Toll Free: (888) 317-4332, Fax: +1-905-890-8562

IDEC ELECTRONICS LIMITED

Unit 2, Beechwood, Chineham Business Park, Basingstoke, Hampshire RG24 8WA, UK
Tel: +44-1256-321000, Fax: +44-1256-327755

E-mail: idec@uk.idec.com

IDEC ELEKTROTECHNIK GmbH Wendenstrasse 331, D-20537 Hamburg, Germany Tel: +49-40-25 30 54 10, Fax: +49-40-25 30 54 24 E-mail: service@idec.de, www.idec.de

IDEC AUSTRALIA PTY. LTD.
2/3 Macro Court, Rowville, Victoria 3178, Australia
Toll Free: 1-800-68-4332, Fax: +61-3-9763-3255
E-mail: sales@au.idec.com

IDEC IZUMI ASIA PTE. LTD.

No. 31, Tannery Lane #05-01, Dragon Land Building, Singapore 347788 Tel: +65-6746-1155, Fax: +65-6844-5995 E-mail: generalinfo@idecasia.com.sg

IDEC IZUMI (H.K.) CO., LTD.

Unit 1505-07, DCH Commercial Centre No. 25, Westlands Road, Quarry Bay, Hong Kong
Tel: +852-2803-8989, Fax: +852-2565-0171

E-mail: idec@idechk.com

IDEC IZUMI (Shanghai) Co., Ltd. Room E, 15F, Majesty Building, No. 138 Pudong Avenue, Shanghai 200120, P.R.C.

Tel: +86-21-5887-9181, Fax: +86-21-5887-8930 E-mail: idec@cn.idec.com

IDEC TAIWAN CORPORATION

8F, No. 79, Hsin Tai Wu Road, Sec. 1, Hsi-Chih, Taipei County, Taiwan Tel: +886-2-2698-3929, Fax: +886-2-2698-3931 E-mail: service@idectwn.com.tw