


Solid State Relays

1-Phase Integrated Heatsink

Zero Cross or Instant On Switching

Types RGC Solid State Contactor 'U' Connection

CARLO GAVAZZI



- Product Width ranging from 17.5mm up to 70mm
- Rated Operational voltage: Up to 600VAC
- Rated Operational current: Up to 85AAC @ 40°C
- Up to 18000A²s for I²t and 1200Vp blocking voltage
- Control voltages: 3-32 VDC, 20-275 VAC (24-190 VDC)
- IP20 protection
- Design according to EN/IEC60947-4-2, EN/IEC60947-4-3, EN/IEC62314, UL508, CSA 22-2 No. 14-10
- Integrated voltage transient protection with varistor
- RoHS compliant
- Short circuit current rating: 100kA
- VDE approval
- Germanischer Lloyd approval¹

Product Description

This new range of solid state contactors presents a unique opportunity to maximize efficiency in panel space and is an evolution of solid state switches for which Carlo Gavazzi is very well known.

Voltage transient protection is standard across the output with a varistor. Specifications are stated at 25°C unless otherwise noted.

1. Germanischer Lloyd approval applicable only to models RGC...15KGU, RGC...20KGU, RGC...25KGU and RGC...30KGU

Ordering Key **RGC 1 A 60 A 40 K G U _**

Solid State Relay	<input type="text"/>
Number of poles	<input type="text"/>
Switching Mode	<input type="text"/>
Rated Operational Voltage	<input type="text"/>
Control voltage	<input type="text"/>
Rated Operational current	<input type="text"/>
Connection type for control	<input type="text"/>
Connection type for power	<input type="text"/>
Connection configuration	<input type="text"/>
Option	<input type="text"/>

Ordering Key (Refer to page 2 for available part numbers)

1Phase SSR with heatsink	Rated Voltage, Blocking Voltage	Control Voltage	Rated Current at 40°C ²	Connection Control	Connection Power	Connection Configuration	Option
RGC1A: ZC⁴	23: 230V +10% - 15%, 800Vp	D: 3 or 4-32VDC	15: 20AAC, 525A ² s 20: 23AAC, 525A ² s 25: 25AAC, 1800A ² s 30: 30AAC, 1800A ² s 40: 40AAC, 3200A ² s 42: 43AAC, 18000A ² s 60: 60AAC, 3200A ² s 62: 65AAC, 18000A ² s 90: 85AAC, 6600A ² s	K: Screw G: Box clamp	G: Box Clamp	U: SSR	P: Overtemperature protection (OTP) ³
RGC1B: IO⁴	60: 600V +10% -15%, 1200Vp	A: 20 - 275VAC, 24-190 VDC					

2. Refer to derating curves

3. Default control connection for RGC..P is Box Clamp. See connections specifications.

4: ZC = Zero Cross switching, IO = Instant On switching

Selection Guide

Rated voltage, Blocking voltage, Switching mode	Control voltage	Connection Control/ Power	Rated operational current @ 40°C (I ² t value)				
			Product width	20 AAC (525A ² s) 17.5mm, low depth	23 AAC (525A ² s) 17.5mm	25 AAC (1800A ² s) 17.5mm, low depth	
230V, 800Vp ZC	3-32VDC 20-275VAC, 24-190VDC	Screw/Box Screw/Box	RGC1A23D15KGU RGC1A23A15KGU	RGC1A23D20KGU RGC1A23A20KGU	RGC1A23D25KGU RGC1A23A25KGU	RGC1A23D30KGU RGC1A23A30KGU	
				40 AAC (3200A ² s) 35mm	43 AAC (18000A ² s) 35mm	60 AAC (3200A ² s) 70mm	65 AAC (18000A ² s) 70mm
	3-32VDC 20-275VAC, 24-190VDC	Screw/Box Screw/Box	RGC1A23D40KGU RGC1A23A40KGU	RGC1A23D42KGU RGC1A23A42KGU	RGC1A23D60KGU RGC1A23A60KGU	RGC1A23D62KGU RGC1A23A62KGU	
				20 AAC (525A ² s) 17.5mm, low depth	23 AAC (525A ² s) 17.5mm	25 AAC (1800A ² s) 17.5mm, low depth	30 AAC (1800A ² s) 22.5mm
600V, 1200Vp ZC	4-32VDC 20-275VAC, 24-190VDC	Screw/Box Screw/Box	RGC1A60D15KGU RGC1A60A15KGU	RGC1A60D20KGU RGC1A60A20KGU	RGC1A60D25KGU RGC1A60A25KGU	RGC1A60D30KGU RGC1A60A30KGU	
				40 AAC (3200A ² s) 35mm	43 AAC (18000A ² s) 35mm	60 AAC (3200A ² s) 70mm	65 AAC (18000A ² s) 70mm
	4-32VDC 20-275VAC, 24-190VDC	Screw/Box Screw/Box	RGC1A60D40KGU RGC1A60A40KGU	RGC1A60D42KGU RGC1A60A42KGU	RGC1A60D60KGU RGC1A60A60KGU	RGC1A60D62KGU RGC1A60A62KGU	
				20 AAC (525A ² s) 17.5mm, low depth	23 AAC (525A ² s) 17.5mm	25 AAC (1800A ² s) 17.5mm, low depth	30 AAC (1800A ² s) 22.5mm
600V, 1200Vp IO	4-32VDC	Screw/Box	RGC1B60D15KGU	RGC1B60D20KGU	RGC1B60D25KGU	RGC1B60D30KGU	
				40 AAC (3200A ² s) 35mm	43 AAC (18000A ² s) 35mm	60 AAC (3200A ² s) 70mm	65 AAC (18000A ² s) 70mm
	4-32VDC	Screw/Box	RGC1B60D40KGU	RGC1B60D42KGU	RGC1B60D60KGU	RGC1B60D62KGU	

Selection Guide - RGC..P (Integrated Overtemperature Protection)

Rated voltage, Blocking voltage, Switching mode	Control voltage	Connection Control/ Power	Rated operational current @ 40°C (I ² t value)		
			Product width	85AAC (6600A ² s) 70mm + fan	85AAC (6600A ² s) 70mm + fan
230V, 800Vp ZC	5-32VDC	Box/Box	RGC1A23D90GGUP		
				40 AAC (3200A ² s) 35mm	60 AAC (3200A ² s) 70mm
600V, 1200Vp ZC	5-32VDC 20-275VAC, 24-190VDC	Box/Box	RGC1A60D40GGUP RGC1A60A40GGUP	RGC1A60D60GGUP RGC1A60A60GGUP	RGC1A60D90GGUP RGC1A60A90GGUP
				85AAC (6600A ² s) 70mm + fan	85AAC (6600A ² s) 70mm + fan
600V, 1200Vp IO	5-32VDC	Box/Box	RGC1B60D90GGUP		

Output Voltage Specifications

	RGC..23..	RGC..60..
Operational Voltage Range	24-240 VAC, +10%, -15% on max	42-600 VAC, +10% -15% on max
Blocking Voltage	800Vp	1200 Vp
Internal Varistor	275V	625V

General Specifications

Latching voltage (across L1-T1)	20V	Over-voltage category	III (fixed installations)
Operational frequency range	45 to 65Hz	Isolation	
Power factor	> 0.5 @ Vrated	Input to Output RGC...	4000 Vrms
Touch Protection	IP20	RGC...D..P	2500 Vrms
Control input status	continuously ON Green LED, when control input is applied	RGC...A..P	4000 Vrms
Pollution degree	2 (non-conductive pollution with possibilities of condensation)	Input and Output RGC...	4000 Vrms
		to case RGC...D..P	4000 Vrms
		RGC...A..P	4000 Vrms
		Input to Fan/ Alarm Output RGC...A..P	2500 Vrms

Output Specifications

	RGC..15..	RGC..20..	RGC..25..	RGC..30..
Rated operational current ⁶				
AC-51 rating @ Ta=25°C	20 AAC	25.5 AAC	30 AAC	30 AAC
AC-51 rating @ Ta=40°C	20 AAC	23 AAC	25 AAC	30 AAC
AC-53a rating @ Ta=40°C	5 AAC	5 AAC	5 AAC	8 AAC
Number of motor starts (x:6, Tx:6s, F:50%) at 40°C ⁵	30	30	30	30
Min. operational current	150 mAAC	150 mAAC	250 mAAC	250 mAAC
Rep. overload current - (Motor Rating) PF = 0.4 - 0.5 UL508: T _{AMB} =40°C, t _{ON} =1s, t _{OFF} =9s, 50cycles	51 AAC	60 AAC	51 AAC	84 AAC
Maximum transient surge current (I _{TSM}), t=10ms	325 Ap	325 Ap	600 Ap	600Ap
Maximum off-state leakage current at rated voltage	3 mAAC	3 mAAC	3 mAAC	3 mAAC
I ² t for fusing (t=10ms) Minimum	525 A ² s	525 A ² s	1800 A ² s	1800 A ² s
Critical dv/dt (@ T _j init = 40°C)	1000 V/us	1000 V/us	1000 V/us	1000 V/us

	RGC..40..	RGC..42..	RGC..60..	RGC..62..	RGC..90..
Rated operational current ⁶					
AC-51 rating @ Ta=25°C	47 AAC	50 AAC	70 AAC	75 AAC	85 AAC
AC-51 rating @ Ta=40°C	40 AAC	43 AAC	60 AAC	65 AAC	85 AAC
AC-53a rating @ Ta=40°C	13 AAC	16 AAC	14.8 AAC	20 AAC	18 AAC
Number of motor starts (x:6, Tx:6s, F:50%) at 40°C ⁵	30	30	30	30	30
Min. operational current	400 mAAC	500 mAAC	400 mAAC	500 mAAC	400 mAAC
Rep. overload current - (Motor Rating) PF = 0.4 - 0.5 UL508: T _{AMB} =40°C, t _{ON} =1s, t _{OFF} =9s, 50cycles	126 AAC	126 AAC	126 AAC	168 AAC	168 ACC
Maximum transient surge current (I _{TSM}), t=10ms	800 Ap	1900 Ap	800 Ap	1900 Ap	1150 Ap
Maximum off-state leakage current at rated voltage	3 mAAC	3 mAAC	3 mAAC	3 mAAC	3 mAAC
I ² t for fusing (t=10ms) Minimum	3200 A ² s	18000 A ² s	3200 A ² s	18000 A ² s	6600 A ² s
Critical dv/dt (@ T _j init = 40°C)	1000 V/us	1000 V/us	1000 V/us	1000 V/us	1000 V/us

5. Overload current profile definition, x: multiple of AC53a rating, Tx: duration of current surge, F: duty cycle

6: refer to Derating Curves

Overtemperature Alarm Specifications for RGC...P

	RGC..D..P	RGC..A..P
Output type	PNP open collector_	Potential Free
Normal state	Closed	Closed
Maximum current rating	50 mADC	50 mADC
Rated voltage (EN61131-2: 2003) ^{7,8} , U _a	24VDC -15%, +20%	24VDC -15%, +20%
Rated voltage, U _s	RGC...D90GGUP	24VDC ± 10%
Fan rating, U _f	RGC...A90GGUP	N/A
Alarm voltage drop	Typical Maximum	2.8VDC 4VDC
Visual Indication	Continous Red LED	Continous Red LED
Reverse polarity protection	24VDC	24VDC

7: DC supply for alarm signal should be supplied from a Class 2 power source

8: Maximum voltage to be applied between 11+ and 12- (U_a) terminals should be 35VDC maximum with reference to A2-

Input specifications


		RGC..D..	RGC..A..
Control voltage range ^{9,10}	RGC..23..	3 - 32 VDC	20 - 275 VAC, 24 (-10%) - 190 VDC
	RGC..60..	4 - 32 VDC	20-275 VAC, 24 (-10%) - 190 VDC
	RGC...P (Uc)	5 - 32 VDC	20-275 VAC, 24 (-10%) - 190 VDC
Pick-up voltage	RGC..23.. RGC..60.. RGC...P	3.0 VDC 3.8 VDC 5 VDC	20 VAC/DC 20 VAC/ 24VDC
Drop-out voltage		1 VDC	5 VAC/DC
Maximum Reverse voltage		32 VDC	-
Response time pick-up ZC (RGC1A..)		0.5 cycle + 500µs @ 24VDC	2 cycles @ 230VAC/110VDC
Response time pick-up IO (RGC1B..)		350µs @ 24 VDC	N/A
Response time drop-out		0.5 cycle + 500µs @ 24VDC	0.5 cycle + 40ms @ 230VAC/ 110VDC
Input current @ 40°C		See diagrams below	See diagrams below

9. DC control to be supplied by class 2 power source according to UL1310


10. For GL approved models control range for RGC1.23... is 4-32VDC and for RGC1.60... 5-32VDC

RG..A..

RGC1 .. A : input current vs input voltage




RGC1 .. A : input current vs input voltage




Input specifications (cont.)

RG..D..



x: Input currents for RGC1..D15, RGC1..D20, RGC1..D25, RGC1..D30, RGC1..D4x, RGC1..D6x




y: input currents valid only for RGC1..D90GGUP

Motor Ratings: HP (UL508) / kW (EN/IEC60947-4-2) @ 40°C

	115 VAC	230 VAC	400 VAC	480 VAC	600 VAC
RGC..15	1/3HP / 0.18kW	1HP / 0.37kW	2HP / 0.75kW	3HP / 1.1kW	3HP / 1.5kW
RGC..20	1/2HP / 0.18kW	1½HP / 0.37kW	2HP / 0.75kW	3HP / 1.1kW	3HP / 1.5kW
RGC..25	1/3HP / 0.18kW	1HP / 0.37kW	2HP / 0.75kW	3HP / 1.1kW	3HP / 1.5kW
RGC..30	¾HP / 0.37kW	2HP / 1.1kW	3HP / 1.5kW	5HP / 2.2kW	5HP / 3.7kW
RGC..40	1HP / 0.56kW	3HP / 1.5kW	5HP / 2.2kW	5HP / 3.7kW	7½HP / 4kW
RGC..42	1½HP / 0.56kW	3HP / 1.5kW	5HP / 2.2kW	7½HP / 3.7kW	10HP / 4kW
RGC..60	1½HP / 0.56kW	3HP / 1.5kW	5HP / 3kW	7½HP / 4kW	10HP / 4kW
RGC..62	2HP / 0.75kW	5HP / 1.5kW	7½HP / 4kW	10HP / 4kW	15HP / 5.5kW
RGC..90	2HP / 0.75kW	5HP / 1.5kW	7½HP / 4kW	10HP / 4kW	15HP / 5.5kW


Detailed Over temperature Alarm Procedure (for RGC...P)




CAUTION

- Alarm condition resets whenever the voltage signal is removed from terminal A1 (+)
- In the case of RGC..D90GGUP, if the voltage signal is not applied across A1(+) and A2 (-) terminals, the overtemperature detection and functionality is lost (including fan operation and alarm signalling)
- In the case of RGC1A60A90GGUP it is necessary to supply IN2 and IN3 with 24VDC for fan operation.
- Alarm procedure for RGC1A60A90GGUP follows 'Alarm signal only' flow since fan is continuously operating.
- Alarm condition automatically resets ONLY when power semiconductor temperature < 80°C
- Temperatures indicated are typical figures.

Output Power Dissipation




Current Derating (UL508)




RGC...P models max. operating temperature is + 70°C

Derating vs. Spacing Curves


RGC.. 15..



RGC.. 20..




RGC.. 25..




Derating vs. Spacing Curves (cont.)


RGC.. 30..



RGC.. 40..




RGC.. 42..




Derating vs. Spacing Curves (cont.)


RGC.. 60..



RGC.. 62..



RGC.. 90GGUP



Agency Approvals and Conformances

Conformance	IEC/EN 62314 IEC/EN 60947-4-2 IEC/EN 60947-4-3	Agency Approvals	UL508 Listed (E172877) cUL Listed (E172877) VDE (0660-109) GL ¹²
	   	Short Circuit Current Rating	100kA, UL508

Electromagnetic Compatibility

EMC Immunity	EN 60947-4-3	Electrical Surge Immunity	IEC/EN 61000-4-5
Electrostatic Discharge (ESD) Immunity	IEC/EN 61000-4-2	(for RGC...UP)	Performance Criteria 1
Air discharge, 8kV	Performance Criteria 1	Output, line to line, 1kV	Performance Criteria 1
Contact, 4kV	Performance Criteria 1	Output, line to earth, 2kV	Performance Criteria 2
Electrical Fast Transient (Burst) Immunity	IEC/EN 61000-4-4	DC lines, line to line, 500V	Performance Criteria 2
Output: 2kV, 5kHz	Performance Criteria 1	DC lines, line to earth, 500V	Performance Criteria 2
Input: 1kV, 5kHz	Performance Criteria 1	Signal lines, line to earth, 1kV	Performance Criteria 2
Electrical Surge Immunity (for RGC...U)	IEC/EN 61000-4-5	Radiated Radio Frequency Immunity	IEC/EN 61000-4-3
Output, line to line, 1kV	Performance Criteria 1	10V/m, 80 - 1000 MHz	Performance Criteria 1
Output, line to earth, 2kV	Performance Criteria 1	10V/m, 1.4 - 2 GHz	Performance Criteria 1
Input, line to line, 1kV	Performance Criteria 2	3V/m, 2 - 2.7 GHz	Performance Criteria 1
Input, line to earth, 2kV	Performance Criteria 2	Conducted Radio Frequency Immunity	IEC/EN 61000-4-6
		10V/m, 0.15 - 80 MHz	Performance Criteria 1
EMC Emission	EN 60947-4-3	Voltage Dips Immunity	IEC/EN 61000-4-11
Radio Interference		0% for 0.5, 1 cycle	Performance Criteria 2
Voltage Emission (Conducted) 0.15 - 30MHz	IEC/EN 60947-4-3 Class A (no filtering needed) IEC/EN 55011 Class A (industrial) with filters - see filter information	40% for 10 cycles	Performance Criteria 2
		70% for 25 cycles	Performance Criteria 2
		80% for 250 cycles	Performance Criteria 2
		Voltage Interruptions Immunity	IEC/EN 61000-4-11
		0% for 5000ms	Performance Criteria 2

EMC Emission	EN 60947-4-3	Radio Interference	
Radio Interference		Field Emission (Radiated)	IEC/EN 55011
Voltage Emission (Conducted) 0.15 - 30MHz	IEC/EN 60947-4-3 Class A (no filtering needed) IEC/EN 55011 Class A (industrial) with filters - see filter information	30 - 1000MHz	Class A (industrial)

Environmental Specifications

Operating Temperature ¹¹	-40°C to 80°C (-40°F to +176°F)	Vibration resistance (2-100Hz, IEC60068-2- 6, EN50155, EN61373)	2g per axis
Storage Temperature	-40°C to 100°C (-40°F to +212°F)	Relative humidity	95% non-condensing @ 40°C
RoHS (2011/65/EU)	Compliant	UL flammability rating (housing)	UL 94 V0
Impact resistance (EN50155, EN61373)	15/11 g/ms		
Weight		RGC..30 (P) RGC..4x (P) RGC..6x (P) RGC..90 (P)	approx 375g (412g) approx 515g (581g) approx 972g (1020g) approx 1100g
RGC..15	approx 260g		
RGC..20 (P)	approx 315g (360g)		
RGC..25 (P)	approx 260g (307g)		

11. Operating temperature range for RGC..P (overtemperature protection) is -30°C to 70°C (-22°F to 158°F)

12. Applicable to models RGC1...15KGU, RGC1...20KGU, RGC1...25KGU and RGC1...30KGU


Filtering - EN / IEC 55011 Class A compliance (for class B compliance contact us)

Part Number	Suggested filter for compliance	Maximum Heater current
RGC1A23..15	68 nF / 275V / X1	20A
RGC1A23..20	68 nF / 275 V / X1	20A
RGC1A23..25, RGC1A23..30	220 nF / 275V / X1	30A
RGC1A23..40	220 nF / 275V / X1 330 nF / 275V / X1	30A 45A
RGC1A23..60	220 nF / 275V / X1 330 nF / 275V / X1	30A 45A
RGC1A23..42, RGC1A23..62	330 nF / 275V / X1	35A
RGC1A23..9x	470 nF / 275V / X1	65A
RGC1A60..15	100 nF / 760V / X1	20A
RGC1A60..20	100 nF / 760V / X1	20A
RGC1A60..25, RGC1A60..30	220 nF / 760V / X1	30A
RGC1A60..40	220 nF / 760V / X1 330 nF / 760V / X1	25A 45A
RGC1A60..60	220 nF / 760V / X1 330 nF / 760V / X1	25A 45A
RGC1A60..42, RGC1A....62, RGC1A....9x	330 nF / 760V / X1 470 nF / 760V / X1	40A 65A


Note:

- Control input lines must be installed together to maintain products' susceptibility to Radio Frequency interference.
- Use of AC solid state relays may, according to the application and the load current, cause conducted radio interferences. Use of mains filters may be necessary for cases where the user must meet E.M.C requirements. The capacitor values given inside the filtering specification tables should be taken only as indications, the filter attenuation will depend on the final application.
- Performance Criteria 1: No degradation of performance or loss of function is allowed when the product is operated as intended.
- Performance Criteria 2: During the test, degradation of performance or partial loss of function is allowed. However when the test is complete the product should return operating as intended by itself.
- Performance Criteria 3: Temporary loss of function is allowed, provided the function can be restored by manual operation of the controls.


Filter Connection Diagrams



Connection Diagram (No OTP)




Connection Diagram (with OTP)




Terminal Layout and Dimensions


RGC...15KGU, RGC..25KGU



RGC...20KGU



RGC...30KGU



1/L1: Supply connection

2/T1: Load connection

A1 (+): Positive control signal

A2 (-): Control ground



⊕ : Protective earth

Housing width tolerance +0.5mm, -0mm...as per DIN43880.



All other tolerances ± 0.5mm. All dimensions in mm.

Terminal Layout and Dimensions

RGC...40KGU, RGC...42KGU



RGC...60KGU, RGC...62KGU



1/L1: Supply connection

2/T1: Load connection

A1 (+): Positive control signal
(Positive supply in case of RGC1A..D90GGUP)

A2 (-): Control ground

IN1: Control signal (only for RGC1A.. D90GGUP)

IN2: Fan + supply (only for RGC1A60A90GGUP)

IN3: Fan - supply (only for RGC1A60A90GGUP)

11 + : Alarm output (+)

OUT, 12 - : Alarm output (-)




⏚ : Protective earth

Housing width tolerance +0.5mm, -0mm...as per DIN43880.





All other tolerances ± 0.5mm. All dimensions in mm.

Terminal Layout and Dimensions (cont.)


RGC...40GGUP, RGC...42GGUP



RGC...60GGUP, RGC...62GGUP






RGC...90GGUP



RGC..D90GGUP

RGC..A90GGUP



1/L1: Supply connection

2/T1: Load connection

A1 (+): Positive control signal
(Positive supply in case of RGC1A..D90GGUP)

A2 (-): Control ground

IN1: Control signal (only for RGC1A.. D90GGUP)

IN2: Fan + supply (only for RGC1A60A90GGUP)

IN3: Fan - supply (only for RGC1A60A90GGUP)

11 + : Alarm output (+)

OUT, 12 - : Alarm output (-)

⊕ : Protective earth


Housing width tolerance +0.5mm, -0mm...as per DIN43880.

All other tolerances ± 0.5mm. All dimensions in mm.

Connection Specifications

POWER CONNECTIONS: 1/L1, 2 /T1

Use 75°C copper (Cu) conductors

	RG..KGU	RG..KGU, RG..GGUP
Stripping Length (X)	12mm	11mm
Connection type	M3.5 screw with box clamp	M5 screw with box clamp
Rigid (Solid & Stranded) UL/ cUL rated data	 1 x 1..6 mm ² 1 x 18.. 10 AWG	 1 x 2.5..25mm ² 1 x 14...3 AWG
Flexible with end sleeve	 1 x 0.5..2.5mm ² 1 x 20.. 14 AWG	 1 x 2.5..16mm ² 1 x 14.. 6 AWG
Flexible without end sleeve	 1 x 1.. 4mm ² 1 x 18.. 12 AWG	 1 x 4.. 25mm ² 1 x 12.. 3 AWG
Torque specifications	 Pozidriv 1 UL: 1.0Nm (8.85lb-in) IEC: 0.9 - 1.1Nm (8 - 9.7lb-in)	 Pozidriv 2 UL: 2.5Nm (22lb-in) IEC: 2.5 - 3.0Nm (22 - 26.6lb-in)

Protective Earth (PE) Connection




1.5Nm (13.3lb-in)

Note: M5 PE screw not provided with SSR. PE connection required when product is intended to be used in Class 1 applications according to EN/IEC 61140.


CONTROL CONNECTIONS: A1(+), A2(-)

Use 60/75°C copper (Cu) conductor

	RG..KGU	
Torque specifications	 M3, Pozidriv 1 UL: 0.5Nm (4.4lb-in) IEC: 0.5 - 0.6Nm (4.4 - 5.3lb-in)	
Stripping Length (X)	 8mm	
Rigid (Solid & Stranded) UL/ cUL rated data	 2 x 0.5..2.5mm ² 2 x 18..12 AWG	 1 x 0.5..2.5mm ² 1 x 18..12 AWG
Flexible with end sleeve	 2 x 0.5..2.5mm ² 2 x 18..12AWG	 1 x 0.5..2.5mm ² 1 x 18..12AWG


CONTROL CONNECTIONS: A1(+), A2(-), IN1, IN2, IN3, 11 (+), 12(-), OUT

Use 60/75°C copper (Cu) conductors

	RG....GGUP	
Torque specifications	 M3, Pozidriv 1 UL: 0.5Nm (4.4lb-in) IEC: 0.4 - 0.5Nm (3.5 - 4.4lb-in)	
Stripping Length (X)	 6mm	
Rigid (Solid & Stranded) UL/ cUL rated data	 2 x 1.0..2.5mm ² 2 x 18..14 AWG	 1 x 1.0..2.5mm ² 1 x 18..14 AWG
Flexible with end sleeve	 2 x 1.0..2.5mm ² 2 x 18..14AWG	 1 x 1.0..2.5mm ² 1 x 18..14AWG

Specifications are subject to change without notice (20.05.2016)

Installation Instructions



Short Circuit Protection

Protection Co-ordination, Type 1 vs Type 2:

Type 1 protection implies that after a short circuit, the device under test will no longer be in a functioning state. In type 2 co-ordination the device under test will still be functional after the short circuit. In both cases, however the short circuit has to be interrupted. The fuse between enclosure and supply shall not open. The door or cover of the enclosure shall not be blown open. There shall be no damage to conductors or terminals and the conductors shall not separate from terminals. There shall be no breakage or cracking of insulating bases to the extent that the integrity of the mounting of live parts is impaired. Discharge of parts or any risk of fire shall not occur.

The product variants listed in the table hereunder are suitable for use on a circuit capable of delivering not more than 100,000A rms Symmetrical Amperes, 600 Volts maximum when protected by fuses. Tests at 100,000A were performed with Class J fuses, fast acting; please refer to the table below for maximum allowed ampere rating of the fuse. Use fuses only.

Tests with class J fuses are representative of Class CC fuses.

Co-ordination type 1 (UL508)

Part No.	Prospective short circuit current [kArms]	Max. fuse size [A]	Class	Voltage [VAC]
RGC..15	100	10	J	max. 600
	100	15	CC	max. 600
RGC..20	100	10	J	max. 600
	100	15	CC	max. 600
RGC..25	100	30	J or CC	max. 600
RGC..30	100	30	J or CC	max. 600
RGC..40	100	40	J	max. 600
RGC..42	100	90	J	max. 600
RGC..60	100	40	J	max. 600
RGC..62	100	90	J	max. 600
RGC..90	100	40	J	max. 600

Co-ordination type 2 (IEC EN 60947-4-2/ -4-3)

Part No.	Prospective short circuit current [kArms]	Ferraz Shawmut		Siba		Voltage [VAC]
		Max fuse size [A]	Part number	Max fuse size [A]	Part number	
RGC..15	10	25	6.9xx CP GRC 14x51 /25	32	50 142 06.32	max. 600
	100	25	6.9xx CP GRC 14x51 /25	32	50 142 06.32	max. 600
RGC..20	10	40	6.6xx CP URD 22x58 /40	32	50 142 06.32	max. 600
	100	40	6.6xx CP URD 22x58 /40	32	50 142 06.32	max. 600
RGC..25	10	40	6.9xx CP GRC 22x58 /40	32	50 142 06.32	max. 600
	100	40	6.6xx CP URD 22x58 /40	32	50 142 06.32	max. 600
RGC..30	10	40	6.9xx CP GRC 22x58 /40	32	50 142 06.32	max. 600
	100	40	6.6xx CP URD 22x58 /40	32	50 142 06.32	max. 600
RGC..40	10	63	6.621 CP URGD 27x60 /63	63	50 194 20.63	max. 600
	10	70	A70QS70-4	63	50 194 20.63	max. 600
	100	63	6.621 CP URQ 27x60 /63	63	50 194 20.63	max. 600
RGC..42	10	63	6.9xx CP URC 14x51 /63	80	50 194 20.80	max. 600
	10	70	A70QS70-4	80	50 194 20.80	max. 600
	100	63	6.9xx CP URC 14x51 /63	80	50 194 20.80	max. 600
	100	70	A70QS70-4	80	50 194 20.80	max. 600
RGC..60 up to 65AAC	10	80	6.621 CP URQ 27x60 /80	80	50 194 20.80	max. 600
	100	n/a	n/a	80	50 194 20.80	max. 600
RGC..62	10	100	6.9xx CP GRC 22x58 /100	100	50 194 20.100	max. 600
	10	100	A70QS100-4	100	50 194 20.100	max. 600
	100	100	6.621 CP URGD 27x60 /100	100	50 194 20.100	max. 600
	100	100	A70QS100-4	100	50 194 20.100	max. 600
RGC..90 up to 80AAC	10	100	6.621 CP URQ 27x60 /100	100	50 194 20.100	max. 600
	10	100	A70QS100-4	100	50 194 20.100	max. 600
	100	n/a	n/a	100	50 194 20.100	max. 600

Type 2 Protection with Miniature Circuit Breakers (M.C.B.s)

Solid State Relay type	ABB Model no. for Z - type M. C. B. (rated current)	ABB Model no. for B - type M. C. B. (rated current)	Wire cross sectional area [mm ²]	Minimum length of Cu wire conductor [m] ¹³
RGC..15, RGC..20	1 pole S201 - Z4 (4A) S201 - Z6 UC (6A)	S201 - B2 (2A) S201 - B2 (2A)	1.0 1.0 1.5	21.0 21.0 31.5
RGC..25, RGC..30	1 pole S201 - Z10 (10A) S201 - Z16 (16A) S201 - Z20 (20A) S201 - Z25 (25A)	S201-B4 (4A) S201-B6 (6A) S201-B10 (10A) S201-B13 (13A)	1.0 1.5 2.5 1.0 1.5 2.5 4.0 1.5 2.5 2.5 4.0	7.6 11.4 19.0 5.2 7.8 13.0 20.8 12.6 21.0 25.0 40.0
	2 pole S202 - Z25 (25A)	S202-B13 (13A)	2.5 4.0	19.0 30.4
RGC..40	1 pole S201 - Z25 (25A)	S201-B13 (13A)	2.5 4.0 6.0	7.0 11.2 16.8
RGC..60	1 pole S201 - Z25 (25A)	S201-B13 (13A)	2.5 4.0 6.0	7.0 11.2 16.8
RGC..90GGUP	1 pole S201 - Z20 (20A) S201 - Z32 (32A) 2 pole S202 - Z20 (20A) S202 - Z32 (32A) S202 - Z50 (50A)	S201-B10 (10A) S201-B16 (16A) S202-B10 (10A) S202-B16 (16A) S202-B25 (25A)	1.5 2.5 4.0 2.5 4.0 6.0 1.5 2.5 4.0 2.5 4.0 6.0 10.0 4.0 6.0 10.0	4.2 7.0 11.2 13.0 20.8 31.2 1.8 3.0 4.8 5.0 8.0 12.0 20.0 14.8 22.2 37.0
RGC..42, RGC..62	1 pole S201-Z32 (32A) S201-Z50 (50A) S201-Z63 (63A)	S201-B16 (16A) S201-B25 (25A) S201-B32 (32A)	2.5 4.0 6.0 4.0 6.0 10.0 16.0 6.0 10.0 16.0	3.0 4.8 7.2 4.8 7.2 12.0 19.2 7.2 12.0 19.2

13. Between MCB and Load (including return path which goes back to the mains).

Note: A prospective current of 6kA and a 230/400V power supply system is assumed for the above suggested specifications. For cables with different cross section than those mentioned above please consult Carlo Gavazzi's Technical Support Group.