## Keysight Technologies

# Streamline Series P924xA USB Oscilloscopes

Compact InfiniiVision 1 GHz Oscilloscope Technology

Data Sheet



## Compact Form. Zero compromise.

Keysight is taking USB instrumentation to a whole new level

Keysight Streamline Series USB oscilloscopes

- P9241A USB oscilloscope 200 MHz bandwidth
- P9242A USB oscilloscope 500 MHz bandwidth
- P9243A USB oscilloscope 1 GHz bandwidth



### Overview

The Keysight Streamline Series P924xA USB oscilloscopes bring the InfiniiVision usability and performance to USB oscilloscopes. Keysight Streamline Series USB oscilloscopes provide maximum investment protection and are built with technology that leverages decades of Keysight's high-performance oscilloscope expertise.

#### Performance

- 200 MHz, 500 MHz or 1 GHz bandwidths available to match your measurement application
- Advanced triggering enables capture and analysis of complex signals
- Visual triggers (zone touch and mask) make trigger and capture of signal errors quick and easy
- Serial protocol analysis and triggering for most common protocols
- Automated FFT and waveform math extend analysis to match your needs
- Segmented memory can analyze 1000 events without ever offloading to a PC

#### Measurement capability

- Support for a variety of probing solutions
  - Differential and single-ended active probes
  - High-voltage probes
- 30+ automated measurements provide simple-to-access analysis

#### Multiple instruments in one

- Oscilloscope support for up to 1 GHz bandwidth with 5 GSa/s
- DVM (Digital voltmeter) 3-digit using the same scope probes
- 8-digit counter for integrated totalizer/frequency counter measurements
- Protocol analyzer for I2C, UART, CAN, LIN, CXPI and more
- Spectrum analysis with FFT and channel power measurements
- 20-MHz arbitrary waveform generator




 $Capturing \ up \ to \ 1,000,000 \ waveforms/sec \ makes \ it \ easy \ to \ find \ anomalies \ like \ this \ glitch \ that \ occur \ very \ rarely.$ 

## **Uncompromising Analysis Capability**

Many USB users have been using digitizer hardware with software that simulates an oscilloscope for test and troubleshoot implementation. The limitations of this configuration are often overlooked, but they can cause signification problems. When a instrument says it has a high waveform update rate, people usually expect it to have a higher probability of catching random and infrequent glitches, but this isn't the case for those instruments. In addition, common measurements like waveform averaging and advanced waveform triggers are not available.

The Keysight Streamline Series USB oscilloscopes USB oscilloscopes require minimum support from a central processing unit (CPU), as most of their core operations are handled by the MegaZoom IV smart memory ASIC, which is Keysight proprietary technology. MegaZoom includes hardware serial decoders and hardware mask/limit testing capability; supports GUI operation; and integrates additional instruments like a WaveGen function/arbitrary waveform generator.





The P924xA USB oscilloscopes utilize hardware to perform many of the functions traditional digitizers do with software on the CPU. By doing more in hardware, P924xA Series oscilloscopes can analyze more of the signal than ever before.

Key to the oscilloscope operation is that the acquisition does the triggering and most of the analysis utilizing onboard hardware. For example, to accomplish 1million waveforms/sec, the waveforms are captured and plotted into hardware on the scope and then the waveform is transferred to the PC for display.

## Industry-exclusive Zone Touch Trigger Makes Triggering Simple

Zone touch triggering eliminates the complexity of setting up advanced triggers. If you have a touch-enabled display on your controller, you can trigger on events by simply drawing a box with your finger on the display of the signal you want to isolate. Keysight pioneered the zone touch trigger, which allows easy capture of difficult-to-define trigger events.





Capturing a serial data stream using a simple edge trigger.

Zone Trigger enable quick and easy isolation of the data pattern of interest.

The P924xAs' high, uncompromised update rate increases your chance of seeing random and infrequent signal anomalies, and zone touch trigger helps you isolate the signals. Now your testing can be faster and more thorough.

### Other touch-based operation

Just like Keysight's touch-enabled InfiniiVision benchtop oscilloscopes (3000T, 4000 and 6000 X-Series), the P924xA Keysight Streamline Series USB oscilloscopes also uses touch capability to interact with signal display. In addition to zone touch trigger, these oscilloscopes also let you move the waveform up/down; adjust the time offset and zoom; and define one of the two touch zone triggers. All that is required is a touch-enabled display connected to your USB scope.

## Additional Software for Added Functionality

# P9240BDLA Application Bundle for Keysight USB oscilloscopes

Take advantage of a new oscilloscope application bundle that will enable ALL software applications (including Wavegen) on your Keysight USB oscilloscope for a huge discount over buying the options individually. See a complete list of applications in Step 2 of the configuration table. (page 10)


# P9240AWGA WaveGen 20 MHz function/arbitrary waveform generator

The P924xA Streamline Series USB oscilloscopes offer a 20-MHz built-in function/arbitrary waveform generator. The WaveGen provides standard stimulus output waveforms to your device under test as well as user-definable frequencies, amplitudes, offset and pulse widths and arbitrary waveform capability. The WaveGen output is routed to a MMCX connector on the front panel of the oscilloscope.

Use the built-in waveform editor to create custom waveforms to output on the oscilloscope's WaveGen. It is also possible to capture a known good or 'golden' waveform on a scope channel and then save that to the ARB so you can generate it to stimulate your system under test.

# P9240FRAA frequency response analyzer

Frequency response analysis is a critical measurement to characterize the stability of feedback networks and switch-mode power supplies. This capability is achieved with a gain and phase measurement versus frequency (Bode plot). By using the waveform generator output to stimulate your design and probing the input and output signals on channels 1 and 2, the oscilloscope provides a clear report on the gain and phase operation of the system.





## Additional Software for Added Functionality (Continued)

### P9240MSKA mask limit testing

With the mask limit testing measurement application, you can quickly test more than 200,000 waveforms per second to a known good waveform with quick go/no-go test results, saving you valuable test time while providing you with more confidence in test results. Test your signals to specified standards, and uncover unexpected signal anomalies.

Mask testing on other oscilloscopes is usually based on software-intensive processing technology, which tends to be slow. Keysight's InfiniiVision oscilloscopes' mask test option is based on hardware-based technology. This means P924xA oscilloscopes can perform more than 200,000 real-time waveform pass/fail tests per second. This provides testing throughput that is orders of magnitude faster than what is available on other oscilloscope mask test solutions, making valid pass/fail statistics almost instantly.



#### P9240VIDA enhanced video/TV application package

The P924XA oscilloscopes support a video IRE display grid, as well as cursors measurements performed in video IRE units for the NTSC and PAL standards. This new capability is standard on P924xA oscilloscopes. The P9240VIDA software provides an array of additional HDTV triggering standards. The additional triggering options provided by the P9240VIDA software speed debug and characterization for engineers working on HDTV video applications.



## Additional Software for Added Functionality (Continued)


### P9240NFCA NFC triggering

Testing NFC-enabled devices is essential during the design validation and manufacturing test phases to ensure quality and reliability of data transmission. This is especially important when you consider that the data being transferred/exchanged between NFC-enabled devices is often secured financial transactions. The P9240NFCA NFC trigger application enables easy configuration to capture the signals of interest for NFC-A, NFC-B and NFC-F messages.

### Decodes

### P9240EMBA embedded serial triggering and analysis (I2C)

The I²C serial decode software option for P924xA Streamline Series USB oscilloscopes displays responsive, time-aligned, on-screen decode of Inter-Integrated Circuit (I²C) serial communication. Because this capability is hardware-based, it provides the fastest throughput solution for triggering on and analyzing I²C serial buses found in a wide variety of embedded designs. You can easily isolate serial packets to find sources of errors due to hardware- or software-related problems. Sometimes it may be necessary to correlate data from one serial bus to another. Keysight's P924xA oscilloscopes can decode two serial buses simultaneously using hardware-based decoding.



## P9240CMPA computer serial trigger/analysis (RS232/422/485/UART)

The RS232/422/485/UART serial triggering and decode option for P924xA oscilloscopes displays responsive, time-aligned, on-screen decode of RS-232/422/485 and other UART serial buses. It provides triggering capabilities on specified transmit or receive values, as well as on parity errors. Trigger on and acquire RS-232/422/485/UART signals using either oscilloscope or logic channels. Hardware-based decode means the scope stays responsive and fast when decode is turned on. Real-time counters continually count transmit and receive frames and errors.

# P9240ATOA automotive serial triggering and analysis (CAN, CAN-dbc, CAN FD, LIN)

The automotive serial triggering and analysis (CAN, LIN) option for P924xA oscilloscopes allows you to trigger on either standard or extended CAN message IDs, including the message ID of a remote transfer request frame. It supports triggering on a data frame and allows you to specify message IDs, data and data length for filtering messages of interest. Triggering on active error frames is also supported. In addition, it supports triggering on LIN frame IDs and data and includes color-coded parity and check sums errors. You can easily isolate serial packets to find sources of errors due to hardware- or software-related problems.



## Decodes (Continued)

# P9240SNSA SENT (single edge nibble transmission) trigger and analysis

The SENT (single edge nibble transmission) is a point-to-point serial bus that interfaces sensors to ECUs and is used primarily in automotive applications. Keysight's P9240SNSA SENT software option for the P924xA Series oscilloscopes provides decoding of fast and slow channel serial data and also offers extensive triggering selections, including the ability to trigger on various error conditions that can accelerate efficiency in debugging this bus.

Keysight's P924xA Streamline USB oscilloscopes can display captured data from multiple buses in a time-interleaved "lister" display. Sometimes it may be necessary to correlate data from one serial bus to another, such as CAN to SENT.

#### P9240CXPA CXPI trigger and decode

CXPI (clock extension peripheral interface) is the next-generation automotive communication protocol intended to reduce the number and weight of wiring harnesses by making multiplexing possible even in advanced, multifunction HMI (human machine interface) automotive systems. In many cases, CXPI is an alternative serial bus used in place of many of today's LIN serial bus applications for automotive body control.

Keysight's P9240CXPA CXPI software for P924xA oscilloscopes provides decoding of standard and long CXPI frames and also offers extensive triggering selections, including the ability to trigger on various error conditions that can accelerate the engineer's efficiency in debugging this bus.

Keysight's P924xA oscilloscopes can display captured data from multiple buses in a time-interleaved "lister" display. This allows correlation of data being passed through gateways, such as CAN to CXPI.

# P9240AROA MIL-STD 1553 and ARINC 429 aerial triggering and analysis

The MIL-STD 1553 serial bus is primarily used to interconnect avionics equipment in military aircrafts. This bus is based on tri-level signaling (high, low and idle) and requires dual-threshold triggering, which the P924xA Streamline Series USB oscilloscopes support. This bus is also implemented as a redundant multi-lane bus (dual-bus analysis), which is also supported.

The ARINC 429 serial bus is used to interconnect avionics equipment in civilian aircrafts. This bus is also based on tri-level signaling (high, low and null) and requires dual-threshold triggering. Since ARINC 429 is a point-to-point bus, multi-lane analysis is also required to capture both send and receive data.



# P9240NRZA user-definable Manchester and NRZ trigger and analysis

Keysight's Manchester and NRZ decode and trigger software supports user-defined protocols, offering flexibility and preventing the need to define multiple specific protocol decoding and triggering. This trigger and decode software application is geared toward automotive customers, who commonly use Manchester and NRZ encoded buses (ex: Profibus PA, DALI, PSI5, etc.).

### P9240UPDA USB power delivery (USB PD) triggering and analysis

The USB Type-C connection has broadened the range of USB usability by incorporating a dynamic power system called USB Power Delivery (USB PD). Negotiating required power between various USB devices is achieved over the USB's Type-C connector's CC line utilizing a serial protocol based on bi-phase marked coding (BMC). The USB PD protocol option (P9240UPDA) for USB oscilloscopes provides an easy way to debug the 300 kbps signal to provide protocol-level debug information of the USB PD serial bus. This option includes enhanced serial analysis capability for decode and listing window view, triggering, and post-acquisition searching



## Configuration

### Step 1. Choose your bandwidth

P9241A – 2 channel, 200 MHz P9242A – 2 channel, 500 MHz P9243A – 2 channel, 1 GHz

# Step 2. Tailor your oscilloscope with integrated capabilities and measurement applications

Model #	Description
P9240AWGA	WaveGen 20 MHz function/arbitrary waveform generator
P9240BDLA	Application bundle includes all applications listed below
P9240FRAA	Frequency response analyzer
P9240MSKA	Mask limit testing
P9240VIDA	Enhanced video/TV Application Package
P9240NFCA	NFC triggering
P9240EMBA	Embedded serial triggering and analysis (I <sup>2</sup> C)
P9240CMPA	Computer serial triggering and analysis (RS232/422/485/UART)
P9240ATOA	Automotive serial triggering and analysis (CAN, CAN-dbc, CAN FD, LIN)
P9240SNSA	SENT (single edge nibble transmission) triggering and analysis
P9240CXPA	CXPI trigger and decode
P9240AROA	MIL-STD 1553 and ARINC 429 serial triggering and analysis
P9240NRZA	User-definable Manchester and NRZ trigger and analysis
P9240UPDA	USB-PD (Power Delivery) triggering and analysis

Software licenses offer multiple options. Typically users purchase the fixed permanent license that enables the software for as long as the oscilloscope is installed where the software license is located. All licenses install on the oscilloscope hardware and will be available regardless of connected PC hardware.

#### There are other alternatives:

- 1. Fixed permanent license (described above)
- 2. Fixed time-based license Enabled license for a limited time period



## Step 3. Choose your probes

The P924xA Series oscilloscopes includes 2 N2843A 500 MHz passive probes.

Other probes are supported but must be purchased as separate products. Please note that only passive probes are supported on the P924xA Streamline Series USB oscilloscopes.

### Probe solutions

Complete family of innovative probes and accessories for the InfiniiVision USB scopes.

Probes	Description	P924xA Oscilloscopes
N2843A	500 MHz 10:1 passive probe	2 included standard with all models
N2842A	300 MHz 10:1 passive probe	Optional
N2841A	150 MHz 10:1 passive probe	Optional
N2840A	50 MHz 10:1 passive probe	Optional
N2894A	700 MHz 10:1 passive probe	Optional
N2142A	75 MHz 1:1, 10:1 switchable passive probe	Optional
N2140A	200 MHz 1:1, 10:1 switchable passive probe	Optional
N2862B	150 MHz 10:1 passive probe	Optional
N2863B	300 MHz, 10:1 passive probe	Optional
N2889A	350 MHz 10:1/1:1 passive probe	Optional
10070D	20 MHz 1:1 passive probe with probe ID	Optional
10076A	250 MHz 100:1, 4 kV high-voltage passive probe	Optional
	with probe ID	
N2791A	25 MHz, ± 700 V high-voltage differential probe	Optional
1146B	1146A 100 kHz, 100 A, AC/DC current probe	Optional
N7040A	23 MHz, 3 kA, AC current probe - Rogowski	Optional
N7041A	30 MHz, 600 A, AC current probe - Rogowski	Optional
N7042A	30 MHz, 300 A, AC current probe - Rogowski	Optional
N7026A	150 MHz high sensitivity clamp-on current probe	Optional

## Performance Characteristics

## P924xA Keysight Streamline Series USB oscilloscopes

P924xA USB oscilloscopes overview				
	P9241A	P9242A	P9243A	
Bandwidth (-3 dB) <sup>1</sup>	200 MHz	500 MHz	1 GHz	
Calculated rise time (10 to 90%)	≤ 1.75 ns	≤ 700 ps	≤ 450 ps	
Input channels	2	2	2	
Maximum sample rate	5 GSa/s one channel,	5 GSa/s one channel, 2.5 GSa/s two channels		
Maximum memory depth	Standard 4 Mpts, standard segmented memory			
Waveform update rate	≥ 1,000,000 waveform	≥ 1,000,000 waveforms/sec <sup>2</sup>		

Vertical system analog channels				
		P9241A	P9242A	P9243A
Hardware bandwidth limits		Approximately 20 MHz (s	electable)	
Input coupling		AC, DC		
Input impedance		Selectable: 1 M $\Omega$ ± 1% (1	5 pF), 50 $\Omega$ ± 3%	
Input sensitivity range		1 mV/div to 5 V/div (1 MΩ	2 and 50 Ω)	1 mV/div to 5 V/div (1 MΩ)
				1 mV/div to 1 V/div (50 Ω)
Vertical resolution		8 bits (measurement reso	olution is 12 bits with averaging)	
Maximum input voltage		135 Vrms		
		Probing technology allow	vs testing of higher voltages. For	example the included N2843A 10:1 probe
		supports testing of up to	300 Vrms.	
DC vertical accuracy		± [DC vertical gain accura	acy + DC vertical offset accuracy	+ 0.21% full scale] <sup>3</sup>
DC vertical gain accuracy 1		± 2.0% full scale		
DC vertical offset accuracy		$\pm$ 0.1 div $\pm$ 2 mV $\pm$ 1% of offset setting		
Channel-to-channel skew		> 100:1 from DC to maximum specified bandwidth of each model (measured with same V/div and		
		coupling on channels)		
Offset range		± 2 V (1 mV/div to 200 m)	V/div)	
		± 50 V (> 200 mV/div to 5 V/div)		
Time base range		2 ns/div to 50 s/div	1 ns/div to 50 s/div	500 ps/div to 50 s/div
Time base accuracy <sup>1</sup>	Pre-trigger	± 1.6 ppm + aging factor	(1st year: ± 0.5 ppm, 2nd year: ±	0.7 ppm, 5 years: ± 1.5 ppm, 10 years:
		± 2.0 ppm)		
Time base delay time range	Post-trigger	Greater of 1 screen width	n or 250 µs	
		1 to 500 s		
Channel-to-channel deskew range		± 100 ns		
Δ Time accuracy (using cursors)		$\pm$ (time base acc. x reading) $\pm$ (0.0016 x screen width) $\pm$ 100 ps		
Modes		Main, Zoom, XY, and Roll		
XY mode		Z Blanking on Ext Trigger	Input, 1.4 V threshold	
		Bandwidth = Max oscilloscope bandwidth, Phase error at 1 MHz < 0.5 degree		

Denotes warranted specifications. All others are typical.
 Requires infinite persistence in order to visually display 1,000,000 wfm/sec.
 Specifications are valid after a 30-minute warm-up period and 1,1000 f. Specifications are valid after a 30-minute warm-up period and ± 10 °C from firmware calibration temperature. 1 mV/div and 2 mV/div are a magnification of 4 mV/div setting. For vertical accuracy calculations, use full scale of 32 mV for 1 mV div and 2 mV/div sensitivity setting.

Acquisition system				
		P9241A	P9242A	P9243A
Maximum analog channels sample rate		5 GSa/s half channel interleav	ved, 2.5 GSa/s all channel	
Maximum analog channels record length		4 Mpts half channel interleave	ed, 2 Mpts all channel	
Acquisition mode	Normal	Default mode		
	Peak detect	Capture glitches as narrow as	250 ps at all-time base s	ettings
	Averaging	Selectable from 2, 4, 8, 16, 64	4, to 65,536	
	High	Real-time boxcar averaging re	educes random noise and	effectively increases vertical resolution to
	resolution	12 bits of resolution when ≥ 1	0 μs/div at 5 GSa/s or ≥ 2	0 μs/div at 2.5 GSa/s
	Segmented			ta streams that have long dead times
		between activity. Maximum so	egments = 1000. Re-arm t	time = 1 μs (minimum time between trigger
		events)		
Time mode	Normal	Default mode		

Trigger system				
	P9241A	P9242A	P9243A	
Trigger sources	Analog channel (1-2)	Analog channel (1-2), external, WaveGen (1 or mod) (FM/FSK)		
Trigger modes	Normal (triggered): R	Requires trigger event for scope to	trigger	
	Auto: Triggers autom	atically in absence of trigger ever	nt	
	Single: Triggers only	once on a trigger event, press [Sir	ngle] again for scope to find another trigger	
	event, or press [Run]	to trigger continuously in either A	auto or Normal mode	
	Force: Trigger immed	liately and display acquisition		
Trigger coupling	DC: DC coupled trigg	er		
	AC: AC coupled trigger, cutoff frequency: < 10 Hz (internal); < 50 Hz (external)			
	HF reject: High-frequency reject, cutoff frequency ~ 50 kHz			
	LF reject: Low-frequency reject, cutoff frequency ~ 50 kHz			
	Noise reject: Selectable OFF or ON, decreases sensitivity 2x			
Trigger holdoff range	40 ns to 10.00 s			
Trigger sensitivity				
Internal <sup>1</sup>	< 10 mV/div: Greater	of 1 div or 5 mV; ≥ 10 mV/div: 0.6	div	
External <sup>1</sup>	200 mVpp from DC to	o 100 MHz		
	350 mVpp 100 to 200 MHz			
Trigger level range				
Any channel	± 6 div from center screen			
External	± 8 V			

 $<sup>1. \</sup>quad \hbox{Denotes warranted specifications. All others are typical}.$ 

Trigger type selections	
	P9241A P9242A P9243A
Zone touch trigger	Trigger on user-defined zones drawn on the display. Applies to one analog channel at a time. Specify zones as either "must intersect" or "must not intersect." Up to two zones. > 200,000 scans/sec update rate
	Supported modes: normal, peak detect, high resolution
	Also works simultaneously with the serial trigger and mask/limit test
Edge	Trigger on a rising, falling, alternating or either edge of any source
Edge then edge (B trigger)	Arm on a selected edge, wait a specified time, then trigger on a specified count of another selected edge
Pulse width	Trigger on a pulse on a selected channel, whose time duration is less than a value, greater than a value, or inside a time
	range Minimum duration setting: 2 ns (500 MHz, 1 GHz), 6 ns (200 MHz)
	Maximum duration setting: 10 s
	Range minimum: 10 ns
Dun+	· · ·
Runt	Trigger on a position runt pulse that fails to exceed a high level threshold. Trigger on a negative runt pulse that fails to
	exceed a low level threshold. Trigger on either polarity runt pulse based on two threshold settings. Runt triggering can
	also be time-qualified (< or >) with a minimum time setting of 2~10 ns and maximum timesetting of 10 s
0	Minimum time setting: 6 ns (200 MHz), 2 ns (500 MHz, 1 GHz)
Setup and hold	Trigger and clock/data setup and/or hold time violation. Setup time can be set from -7 to 10 s. Hold time can be set from 0 s to 10 ns
Rise/fall time	Trigger on rise-time or fall-time edge speed violations (< or >) based on user-selectable threshold
	Select from (< or >) and time settings range between
	Minimum: 1 ns (500 MHz, 1 GHz), 3 ns (200 MHz)
	Maximum: 10 s
N <sup>th</sup> edge burst	Trigger on the Nth (1 to 65535) edge of a pulse burst. Specify idle time (10 ns to 10 s) for framing
Pattern	Trigger when a specified pattern of high, low and don't care levels on any combination of analog or trigger channels is
	[entered   exited]. Pattern must have stabilized for a minimum of 2 ns to qualify as a valid trigger condition
	Minimum duration setting: 2 ns (500 MHz, 1 GHz), 6 ns (200 MHz)
	Maximum duration setting: 10 s
	Range minimum: 10 ns
Or	Trigger on any selected edge across multiple analog channels
Video	Trigger on all lines or individual lines, odd/even or all fields from composite video or broadcast standards (NTSC, PAL,
Vidoo	SECAM, PAM-M)
Enhanced Video (optional)	Trigger on lines and fields of enhanced and HDTV standards (480p/60, 567p/50, 720p/50, 720p/60, 1080p/24,
	1080p/25, 1080p/30, 1080p/50, 1080p/60, 1080i/50, 1080i/60)
I <sup>2</sup> C (optional)	Trigger at a start/stop condition or user defined frame with address and/or data values. Also trigger on missing acknowl-
	edge, address with no accq, restart, EEPROM read, and 10-bit write
RS-232/422/485/UART	Trigger on Rx or Tx start bit, stop bit or data content or parity error
(optional)	
CAN (optional)	Trigger on CAN (controller area network) version 2.0A,2.0B, and CAN-FD (flexible data-rate) signals. Trigger on the start of
o, (op	frame (SOF), the end of frame (EOF), data frame ID, data frame ID and data (non-FD), data frame ID and data (FD), remote
	frame ID, remote or data frame ID, error frame, acknowledge error, from error, stuff error, CRC error, spec error (ack or
	form or stuff or CRC), all errors, BRS bit (FD), CRC delimiter bit (FD), ESI bit active (FD), ESI bit passive (FD), overload
	frame., message, message and signal (non-FD), message and signal (FD, first 8 bytes only)
LIN (optional)	Trigger on LIN (local interconnect network) sync break, sync frame ID, or frame ID and data, parity error, checksum error,
την (υριισπαι)	frame (symbolic), frame and signal (symbolic)
MIL-STD 1553 (optional)	Trigger on MIL-STD 1553 signals based on word type (data or command/status), remote terminal address, data and errors
(ייייייייייייייייייייייייייייייייייייי	
ADINIC (20 (antional)	(parity, sync, Manchester encoding)
ARINC 429 (optional)	Trigger and decode on ARINC429 data. Trigger on word start/stop, label, label + bits, label range, error conditions (parity,
	word, gap, word or gap, all), all bits (eye), all 0 bits, all 1 bits

Trigger type selection	ns (Continued)			
	P9241A	P9242A	P9243A	
SENT (optional)	slow channel message	Trigger and decode on SENT bus, start of fast channel message, start of slow channel message, fast channel SC and data, slow channel message ID, slow channel message ID and data, tolerance violation, fast channel CRC error, slow channel CRC error, all CRC errors, pulse period error, successive sync pulses error (1/64)		
CXPI (optional)	Trigger and decode on CXPI data. Trigger on frame, PTYPE, frame ID or error by type. Decodes all message types and errors			
NFC (optional)	Trigger for NFC-A, NFC	C-B,and NFC-F		

Waveform measu	rements		
		P9241A P9242A P9243A	
Cursors		Single cursor accuracy: ± [DC vertical gain accuracy + DC vertical offset accuracy + 0.21% fu	ıll scale]
		Dual cursor accuracy 1: ± [DC vertical gain accuracy + 0.42% full scale]	
		Units: Seconds(s), Hz (1/s), phase (degrees), ratio (%)	
Automatic measur	rements	Measurements continuously updated with statistics. Cursors track last selected measureme	nt.
		Select up to eight measurements from the list below:	
		<ul> <li>Snapshot all: Measure all single waveform measurements (31)</li> </ul>	
		- Voltage: Peak-to-peak, maximum, minimum, amplitude, top, base, overshoot, pre-shoot	t,
		average-N cycles, average-full screen, DC RMS-N cycles, DC RMS-full screen, AC RMS	5-N
		cycles, AC RMS-full screen (std deviation), ratio-N cycle, ratio-full screen	
		- Time: Period, frequency, counter, + width, - width, burst width, +duty cycle, -duty cycle	, bit
		rate, rise time, fall time, delay, phase, X at min Y, X at max Y	
		- Count: Positive pulse count, negative pulse count, rising edge count, falling edge count	
		- Mixed: Area-N cycles, area-full screen	
Automatic measur	rement logging	Available via BenchVue	
Counter		Built-in frequency counter	
		Source: On any analog	
		Resolution: 8 digits	
		Maximum frequency: Bandwidth of scope	
Waveform math			
Number of math fu	unctions	Two, displays FFT and one math simultaneously. Can be cascaded	
Arithmetic		Add, subtract, multiply, divide, differentiate, integrate, FFT, Ax + B, squared, square root, abs	
		value, common logarithm, natural logarithm, exponential, base 10 exponential, low pass filte	
		pass filter, averaged value, smoothing, envelope, magnify, max hold, min hold, measurement	trend,
		chart logic bus (timing or state)	
Enhanced FFT	Record size	Up to 64 kpts resolution	
	Window types	Hanning, Flat Top, Rectangular, Blackman-Harris	
	Time gated FFT	Gate the time range of data for FFT analysis in the zoom view. For time and frequency domain	١
		correlated analysis	
	Waveforms	FFT, max hold, min hold, average	
	Peak search	Max 11 peaks, threshold and excursion control	
	Channel power	Power across one frequency range	
	Occupied bandwidth	Percentage of the total power, centered on an assigned channel frequency as specified by us	
	Adjacent channel power	Ratio the power in the main frequency range to the power contained in one or more sidebanc	ds
	ratio		
	Total harmonic distortion	Ratio the power in the fundamental frequency to the power contained in the rest of the harm	onics
		and noise	

 $<sup>1. \</sup>quad \hbox{Denotes warranted specifications. All other are typical}.$ 

Search, navigate a	nd lister			
		P9241A	P9242A	P9243A
Туре		Edge, pulse width, ris	e/fall, runt, frequency peak, seria	ıl bus 1, serial bus 2
Сору		Copy to trigger, copy from trigger		
Frequency peak	Source	Math functions		
Max # of Peaks		11		
	Control	Results order in frequ	ency or amplitude	
Result display Event lister or navigation. Manual or auto scroll via navigation or touch event		igation or touch event lister entry to jump to a		
		specific event		

WaveGen - Built-in func	tion/arbitrary waveform generator (specifications are typical) P9241A P9242A	P9243A			
WaveGen out	Front-panel MMCX connector	1 02-101			
Waveforms	Sine, square, ramp, pulse, DC, noise, sine cardinal (sinc), exponential arbitrary	rise, exponential fall, cardiac, Gaussian pulse and			
Modulation	Modulation types: AM, FM, FSK				
	Carrier waveforms: Sine, ramp, sine cardinal, exponential rise, expon	ential fall and cardiac			
	Modulation source: Internal (no external modulation capability)				
	AM:				
	<ul> <li>Modulation: sine, square, ramp</li> </ul>				
	<ul> <li>Modulation frequency: 1 Hz to 20 kHz</li> </ul>				
	<ul><li>Depth: 0 to 100%</li></ul>				
	FM:				
	<ul> <li>Modulation: sine, square, ramp</li> </ul>				
	<ul> <li>Modulation frequency: 1 Hz to 20 kHz</li> </ul>				
	<ul> <li>Minimum carrier frequency: 10 Hz</li> </ul>				
	<ul> <li>Deviation: 1 Hz to carrier frequency or (2e12/carrier frequency), whichever is smaller</li> </ul>				
	FSK:				
	<ul> <li>Modulation: 50% duty cycle square wave</li> </ul>				
	<ul><li>FSK rate: 1 Hz to 20 kHz</li></ul>				
	<ul> <li>Hop frequency: 2 x FSK rate to 10 MHz</li> </ul>				
Sine	Frequency range: 0.1 Hz to 20 MHz				
	Amplitude flatness: ± 0.5 dB (relative to 1 kHz)				
	Harmonic distortion: -40 dBc				
	Spurious (non harmonics): –40 dBc				
	Total harmonic distortion: 1%				
	SNR (50 $\Omega$ load, 500 MHz bandwidth): 40 dB (Vpp > = 0.1 V); 30 dB (	Vpp < 0.1 V)			
Square wave /pulse	Frequency range: 0.1 Hz to 10 MHz				
	Duty cycle: 20 to 80%				
	Duty cycle resolution: Larger of 1% or 10 ns				
	Pulse width: 20 ns minimum				
	Rise/fall time: 19 ns (10 to 90%)				
	Pulse width resolution: 10 ns or 5 digits, whichever is larger				
	Overshoot: < 2%				
	Asymmetry (at 50% DC): ± 1% ± 5 ns				
	Jitter (TIE RMS): 500 ps				
Ramp/triangle wave	Frequency range: 0.1 Hz to 200 kHz				
	Linearity: 1%				
	Variable symmetry: 0 to 100%				
	Symmetry resolution: 1%				

	P9241A	P9242A	P9243A		
Noise	Bandwidth: 20 MHz typical				
Sine cardinal (sinc)	Frequency range: 0.1 Hz to 1.0	) MHz			
Exponential rise/fall	Frequency range: 0.1 Hz to 5.0	) MHz			
Cardiac	Frequency range: 0.1 Hz to 20	0.0 kHz			
Gaussian pulse	Frequency range: 0.1 Hz to 5.0	) MHz			
Arbitrary	Waveform length: 1 to 8k poin	its			
	Amplitude resolution: 10 bits (	(including sign bit) <sup>1</sup>			
	Repetition rate: 0.1 Hz to 12 M	1Hz			
	Sample rate: 100 MSa/s				
	Filter bandwidth: 20 MHz				
requency	Sine wave and ramp accuracy	:			
	<ul> <li>130 ppm (frequency &lt; 10</li> </ul>	kHz)			
	<ul><li>50 ppm (frequency &gt; 10 kHz)</li></ul>				
	Square wave and pulse accuracy:				
	- [50+frequency/200] ppm (frequency < 25 kHz)				
	<ul><li>50 ppm (frequency ≥ 25 kHz)</li></ul>				
	Resolution: 0.1 Hz or 4 digits, whichever is larger				
Amplitude	Range:				
	<ul><li>20 mVpp to 5 Vpp into Hi-Z</li></ul>				
	$-10$ mVpp to 2.5 Vpp into 50 $\Omega$				
	Resolution: 100 μV or 3 digits, whichever is higher				
	Accuracy: 2% (frequency = 1 k	kHz)			
DC offset	Range:				
	$-\pm 2.5 \text{ V}$ into Hi-Z				
	$-$ ± 1.25 V into 50 $\Omega$				
	Resolution: $100\mu\text{V}$ or $3$ digits, whichever is higher				
	Accuracy (waveform modes): $\pm$ 1.5% of offset setting $\pm$ 1% of amplitude $\pm$ 1 mV				
	Accuracy (DC mode): ± 1.5% of offset setting ± 3 mV				
rigger output	Trigger output available on trig out MMCX				
Main output	Impedance: 50 Ω typical				
	Isolation: Not available				
	Protection: Overload automat	ically disables output	·		
Output mode	Normal				
	Single-shot (arbitrary, sine, ra	mp, sine cardinal, exp rise/fall, cardiac, Gaussian pu	lse)		

<sup>1.</sup> Full resolution is not available at output due to internal attenuator stepping.

Note: Gaussian pulse: 4 Vpp maximum into Hi-Z; 2 Vpp maximum into 50  $\Omega$ .

Digital voltmeter (specifications are typical)			
	P9241A	P9242A	P9243A
Functions	ACrms, DC, DCrms		
Resolution	ACV/DCV: 3 digits		
Measuring rate	100 times/second		
Autoranging	Automatic adjustment of	Automatic adjustment of vertical amplification to maximize the dynamic range of measurements	
Range meter	Graphical display of mo	Graphical display of most recent measurement, plus extrema over the previous 3 seconds	

Precision counter	r/totalizer (specifications a	re typical)			
		P9241A	P9242A	P9243A	
Counter	Source	Any analog channel o	Any analog channel or trigger qualified event		
	Resolution	8 digits (for trigger q	8 digits (for trigger qualified event)		
	Max frequency	1 GHz	1 GHz		
	Trig qual events	1/(trigger hold off tin	1/(trigger hold off time) for trigger qualified events (max 25 MHz, minimum dead time of 40 ns)		
Measurement		Frequency, period, to	talize		
Totalizer	Counter size	64-bit totalizing cou	64-bit totalizing counter		
	Edge	Rise or fall	Rise or fall		
	Gating	Positive or negative l	evel. Select from analog channels	except the source	

## Connectivity

Physical and virtual connections			
	P9241A	P9242A	P9243A
Probe	50 Ω /1 ΜΩ		
WaveGen connector	MMCX		
External trigger	MMCX 30Vrms/60Vdc max		
Auxiliary output	MMCX		
Reference I/O	MMCX		

## General and Environmental Characteristics

General and environmental			
	P9241A	P9242A	P9243A
Power consumption	35 W (typical) power from included external p	ower adapter (no power is used from the	e USB connection)
	+ 3.3 V 3.2 A (typical)		
	+ 12 V 2.0 A (typical)		
	Operating	Storage	
Temperature	0 to 55 °C	–40 to 70 °C	
Altitude	Up to 3000 m	Up to 4500 m	
Humidity	Type tested 95% RH @ 40C non-condensing (on second line) decreasing linearly to 50% RH at 55 °C		
Dimensions	177 mm X 335 mm X 50 mm (WxDxH)		
Weight	2.5 Kg		
Safety	UL61010-1 3rd edition, CAN/CSA-C22.2 No.	61010-1-12	
Electromagnetic compatibility	Meets EMC directive (2004/108/EC), meets of	r exceeds IEC 61326-1:2005/EN61326-	1:2013 (basic)
	IEC 61000-4-2/EN 61000-4-2		
	IEC 61000-4-3/EN 61000-4-3		
	IEC 61000-4-4/EN 61000-4-4		
	IEC 61000-4-5/EN 61000-4-5		
	IEC 61000-4-6/EN 61000-4-6		
	IEC 61000-4-8/EN 61000-4-8		
	IEC 61000-4-11/EN 61000-4-11		
	Canada: ICES/NMB-001:2006		
	Australia/New Zealand: AS/NZS CISPER 11:2	011	

System requirements			
	P9241A	P9242A	P9243A
Operating systems	Windows 10 (64-bit)		
	Windows 7 SP1 (64-bit)		
Processor speed	1 GHz 64-bit (x64)		
Memory	Available memory 1.5 GB minimum		
Disk	Available disk space 2.5 GB available hard disk space		
Required application	Keysight IO Libraries Suite 2018 Update 1.0		
	Microsoft .NET Framework		
Display minimum	1024 x 768, 96 or 120 DPI		

Included standard with oscilloscope				
	P9241A	P9242A	P9243A	
Calibration	2 year			

## Related literature

Publication title	Publication number
Mask/Waveform Limit Testing For InfiniiVision Series Oscilloscopes - Data Sheet	5990-3269EN
Serial Bus Options for InfiniiVision X-Series Oscilloscopes - Data Sheet	5990-6677EN
Triggering on Infrequent Anomalies and Complex Signals using Zone Trigger - Application Note	5991-1107EN
Using an Oscilloscope Time Gated Fast Fourier Transforms for Time Correlated Mixed Domain Analysis - Application Note	5992-0244EN

#### **Evolving Since 1939**

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.







#### myKeysight

#### myKeysight

#### www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

#### http://www.keysight.com/find/emt\_product\_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES Accelerate Technology Adoption. Lower costs.

#### **Keysight Services**

#### www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—onestop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.



#### Keysight Assurance Plans

#### www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

#### Keysight Channel Partners

#### www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

www.keysight.com/find/usb-scopes

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

#### **Americas**

Canada (877) 894 4414 Brazil 55 11 3351 7010 Mexico 001 800 254 2440 United States (800) 829 4444

#### Asia Pacific

Australia 1 800 629 485 China 800 810 0189 800 938 693 Hong Kong 1 800 11 2626 India Japan 0120 (421) 345 080 769 0800 Korea Malaysia 1 800 888 848 Singapore 1 800 375 8100 0800 047 866 Taiwan Other AP Countries (65) 6375 8100

#### Europe & Middle East

For other unlisted countries: www.keysight.com/find/contactus (BP-9-7-17)

Opt. 3 (IT)

0800 0260637



United Kingdom

#### www.keysight.com/go/quality

Keysight Technologies, Inc. DEKRA Certified ISO 9001:2015 Quality Management System

This information is subject to change without notice. © Keysight Technologies, 2017 - 2018 Published in USA, May 14, 2018 5992-2897EN



