LBW Flush Mount 22mm Switches & Pilot Lights

Flush bezel projects only 2mm from front of panel. Removable contact blocks are ideal for single board mounting.

Key Features

- · Pushbuttons, illuminated pushbuttons, selector switches, and key selector switches with up to 3PDT contacts.
- Key selectors with keys that are difficult to duplicate. Seven different key numbers to choose from.
- Pilot lights with round or square flat lenses.
- Solder / Tab or PC Board terminal.
- Black or metallic flush bezels available.
- Guard pushbuttons, illuminated or non-illuminated are available.
- Illuminated pushbuttons with bright, clear, ring, flush or extended lens.
- Choice of either gold-clad or silver contacts.
- Degree of protection: IP65 (from the front of the panel).

Applicable Standards	Mark	File No. or Organization
UL508	<i>71</i> 2	UL Recognition No.E55996
CSA 22.2 No.14	(1)	CSA File No. LR 21451
FN60947-5-1		TÜV Rheinland
EN00947-3-1	CE	EU Low Voltage Directive
GB14048.5	@	

Specifications

Shecilica	เนบแจ	
Operating Temperature Storage Temperature		-25 to +60°C (no freezing), Illuminated units: -25 to +55°C
		-30 to +80°C (no freezing)
Operating H	umidity	45 to 85% RH (no condensation)
Contact Res	istance	50 mW maximum (initial value)
Insulation R	esistance	100 MW minimum (500V DC megger)
Dielectric Strength	Switch	Between live part and ground: 2,000V AC, 1 min. Between terminals of different poles: 2,000V AC, 1 min. Between terminals of the same poles: 1,000V AC, 1 min.
Ü	Illumination	Between live part and ground: 2,000V AC, 1 min.
Vibration Re	sistance	Operating extremes/Damage limits: 5 to 55 Hz, amplitude 0.5mm
Shock Resis	tance	Operating extremes: 100 m/s ² Damage limits: 1,000 m/s ²
Mechanical Life (minimum operations) Electrical Life (minimum operations)		Momentary: 2,000,000 Maintained: 250,000 Selector switches: 250,000 Key selector switches: 250,000
		Momentary: 50,000 / 100,000 ¹ Maintained: 50,000 / 100,000 ² Selector switches: 50,000 / 100,000 ² Key selector switches: 50,000 / 100,000 ²
Degree of P	rotection	IP65 (IEC 60529)
Terminal Style Bezel Weight (approx.)		Solder/tab terminal #110, PC board terminal
		Black plastic or metallic
		16g (illuminated puthbutton) 14g (pilot light) 15g (pushbutton) 17g (selector switch) 29g (key switch) 17g (illuminated pushbutton with guard) 18g (push button with guard)

- 1. Switching frequency 1,800 operations/h.
- 2. Switching frequency 1,200 operations/h.



Contact Ratings

oontaot natingo				
Gold Contact (switch base color: blue)				
Rated Insulation Voltage	250V			
Rated Thermal Current	3A			
Rated Operating Voltage	30V DC	125V AC		
Rated Operating Current (resistive load)	0.1A	0.1A		
Contact Material	Gold-clad silve	er		

Minimum applicable load (reference value): 5V AC/DC, 1 mA						
Silver Contact (switch base color: gray)						
Rated Insulation Voltage	Rated Insulation Voltage			250V		
Rated Operating Voltage	ge		30V	125V	250V	
	AC	Resistive load	_	5A	5A	
	50/60Hz	Inductive load	_	ЗА	1.5A	
	DC	Resistive load	5A	1.1A	_	
Rated Operating		Inductive load	2.5A	0.55A	_	
Current	AC 50/60Hz	Resistive load	_	5A	3A	
		Inductive load	_	ЗА	1.5A	
	DC	Resistive load	3A	0.6A	_	
		Inductive load	1A	0.22A	_	
Rated Thermal Current	Rated Thermal Current		5A			
Contact Material	ontact Material		Silver			

AC inductive load: PF=0.6 to 0.7 DC inductive load: L/R=7 ms max.

LED Ratings

LED Katings			
Rated Voltage	5V DC	12V AC/DC	24V AC/DC
Voltage Range	5V DC±5%	12V AC/DC±10%	24V AC/DC ±10%
LED Part No.	LB9Z-LED5@	LB9Z-LED1@	LB9Z-LED2@
Rated Current	A, R: 22 mA G, PV	V, S: 16 mA	
Voltage Rating	Marked on the side	of the LED unit	
LED Life (reference value)	Approx. 30,000 hours (until the brightness reduces to 50% of the initial value)		
	A, PW, R	A, PW, R	
Internal	X10 X10 X2 (-)	X10————————————————————————————————————	
Circuit	G, S	G, S	
	X10 X10 X2 X10 (-)	X10————————————————————————————————————	LED Chip Protection Diode Floating Protection Diode Floating Varietor

- 1. For @ (color code): A (amber), G (green), PW (white), R (red), S (blue)
 - Use the white LED for yellow illumination.
- 3. LED lamp contains a current-limiting resistor.



Illuminated Pushbuttons (Assembled)



- Flush/Extended color code: A (amber), G (green), PW (pure white), R (red), S (blue), Y (yellow)
- Ring-illuminated color code: PW (pure white), WA (amber), WG (green), WR (red), WS (blue)
- Illuminated pushbuttons contain an LED unit. For details on LED units, see 580.
- . The guard opens 180 degrees spring-return.
- Illuminated pushbuttons can be used with legend markings. Engraving can be done on a marking plate which is placed in the lens, or a clear film can be
 printed and placed in the lens. See 594 for details on the marking plate and film.
- White lens type (when light is off) are available. Clear lens is used instead of colored lens for amber, green, red, and blue illuminated pushbuttons. Amber, green, red, or blue LED units are used. To specify, see Part Number Interpretation below.
- PC board terminals available for gold contacts. Silver contacts also available. To specify, see Part Number Interpretation below.
- Extended style is available. See Part Number Interpretation below (3).
- Flush ring-illuminated style is available. See Part Number Interpretation below (3). Guard is not available with flush ring-illuminated style.
- 5V DC and 12V AC/DC LED operating voltages also available.
- Marking plates are available. See accessory section.

Part Number Interpretation

LBW1L-23T456*



To be used for interpreting part numbers only, not for part number development.

① Style

Code	Shape
6	Round / Black Bezel
7	Square / Black Bezel
6M	Round / Metallic Bezel
7M	Square / Metallic Bezel
6G	Round with Guard
7G	Square with Guard

② Operation

e oporation				
Code	Operation			
Α	Maintained			
М	Momentary			

③ Operator Style

Code	Operator Style		
1	Flush		
2	Extended		
1R	Flush Ring-illuminated		

^{*} Extended style is available only for round (black/metallic bezel) and in momentary operation. Guard model is not available.

④ Contacts

Code	Contact
1	Gold/SPDT
2	Gold/DPDT
5	Silver/SPDT
6	Silver/DPDT

5 LED Operating Voltage

Code	Rated Operating Voltage
1	5V DC
3	12V AC/DC
4	24V AC/DC

6 Others

Code	Specification	Part No. Example
	Solder/Tab Terminal	_
V	PC Board Terminal (Gold Contact Only)	LBW6L-M1T14 <u>V</u> *

[•] Specify the color code in place of * in the table above.

Illuminated Pushbuttons (Sub-assembled)

Contact Block	Operator	LED Module	Lens	Completed Unit
	•	N I		

Contact Block

Terminal Style		Material	Contact	Part Number
	Calday/Tab		SPDT	LB-T50
	Solder/Tab		DPDT	LB-T60
	PCB	Gold	SPDT	LB-T10V
PCB			DPDT	LB-T20V

LED Module

Amhar		
Amber	5V	LB9Z-LED5A
	12V	LB9Z-LED1A
	24V	LB9Z-LED2A
Green	5V	LB9Z-LED5G
	12V	LB9Z-LED1G
	24V	LB9Z-LED2G
Red	5V	LB9Z-LED5R
	12V	LB9Z-LED1R
	24V	LB9Z-LED2R
Blue	5V	LB9Z-LED5S
	12V	LB9Z-LED1S
	24V	LB9Z-LED2S
Pure	5V	LB9Z-LED5PW
vviile	12V	LB9Z-LED1PW
	24V	LB9Z-LED2PW
	Red	24V Green 5V 12V 24V Red 5V 12V 24V Blue 5V 12V 24V Pure 5V White 5V

Operator

Operator				
Style	Mounting Style	Shape	Momentary	Maintained
TO THE	Flush Mount	Round	LBW6L-M0	LBW6L-A0
	(Plastic)	Square	LBW7L-M0	LBW7L-A0
	Flush Mount (Metallic)	Round	LBW6ML-M0	LBW6ML-A0
		Square	LBW7ML-M0	LBW7ML-A0
100	Flush Mount (Built-in switch guard)	Round	LBW6GL-M0	LBW6GL-A0
		Square	LBW7GL-M0	LBW7GL-A0
	Flush Mount (Plastic) Flush Mount (Metallic)	Round (for	LBW6L-M20	LBW6L-A20
		extended lens)	LBW6ML-M20	LBW6ML-A20

Lens

Shape	Color	Part Number
	Amber	LBW6A-L1A
Round (Flush)	Green	LBW6A-L1G
	Red	LBW6A-L1R
	Blue	LBW6A-L1S
	White	LBW6A-L1W
	Yellow	LBW6A-L1Y
Pound (Extended)	Amber	LBW6A-L2A
Round (Extended)	Green	LBW6A-L2G
	Red	LBW6A-L2R
	Blue	LBW6A-L2S
	White	LBW6A-L2W
	Yellow	LBW6A-L2Y
Square (Flush)	Amber	LBW7A-L1A
	Green	LBW7A-L1G
	Red	LBW7A-L1R
2	Blue	LBW7A-L1S
	White	LBW7A-L1W
	Yellow	LBW7A-L1Y
Round Ring Flush	White	LBW6A-L1R-W
Square Ring Flush	White	LBW7A-L1R-W

Note: No marking plate used in ring illuminated pushbottons.



□16.4


□26


Ring-illuminated

Dimensions All dimensions in mm.

Switches & Pilot Devices


Flush/Ring-illuminated





Locking Ring

Terminal Arrangement (Bottom View)



- For details on pc board and circuit design, see 594.
- For details on single board mounting, see 593.



Relays & Sockets

Pilot Lights

LBW1P-1T023*

Part No.



Round / Black Bezel Square / Black Bezel







Square / Metallic Bezel

① Style	③ LED Operating Voltage	Part No.	* Illumination Color Code
Black Bezel	24V AC/DC	LBW①P-1T04*	Specify the color code in place of * in the Part No. A: amber G: green
Metallic Bezel	24V AC/DC	LBW①P-1T04*	PW: pure white R: red S: blue Y: yellow

- Pilot lights contain an LED unit. For maintenance LED units see 583.
- Legends and symbols can be engraved on a marking plate or film to be inserted under the lens by users for labelling purposes. See 596 for details.
- White lens type (when light is off) are available. Clear lens is used instead of colored lens for amber, green, red, and blue pilot lights. Amber, green, red, or blue LED units are used. To specify, see Part Number Interpretation below.
- PC board terminals available. To specify, see Part Number Interpretation below.
- 5V DC and 12V AC/DC LED operating voltages also available.

Part Number Interpretation

LBW1P-1T023*



To be used for interpreting part numbers only, not for part number development.

① Style

Code	Shape
6	Round / Black Bezel
7	Square / Black Bezel
6M	Round / Metallic Bezel
7M	Square / Metallic Bezel

② LED Operating Voltage

Code	Rated Operating Voltage
1	5V DC
3	12V AC/DC
4	24V AC/DC

3 Others

Code	Specification	Part No. Example
Blank	Solder/Tab Terminal	_
V	PC Board Terminal	LBW6P-1T04 <u>V</u> *

• Specify the color code in place of * in the table above.



Pilot Lights (Sub-assembled)

Switches & Pilot Devices

Contact Block	Operator	LED Module	Lens	Completed Unit
		N X	+	

Contact Block

Terminal Style		Part Number
	Solder Tab	LB-T00
	PCB	LB-T00V

LED Module

Style	Color	Voltage	Part Number
		5V	LB9Z-LED5A
	Amber	12V	LB9Z-LED1A
		24V	LB9Z-LED2A
		5V	LB9Z-LED5G
	Green	12V	LB9Z-LED1G
- 4		24V	LB9Z-LED2G
1000		5V	LB9Z-LED5R
Section 1	Red	12V	LB9Z-LED1R
25		24V	LB9Z-LED2R
1	Blue	5V	LB9Z-LED5S
		12V	LB9Z-LED1S
		24V	LB9Z-LED2S
	D	5V	LB9Z-LED5PW
	Pure White	12V	LB9Z-LED1PW
	VVIIIC	24V	LB9Z-LED2PW

Operator

Style	Mounting Style	Shape	Part Number
9	Flush Mount (Plastic)	Round	LBW6P-0
		Square	LBW7P-0
Flush Mount (Metallic)	Flush Mount	Round	LBW6MP-0
	(Metallic)	Square	LBW7MP-0

Lens

Shape	Color	Part Number
Round	Amber	LBW6A-P1A
	Green	LBW6A-P1G
	Red	LBW6A-P1R
	Blue	LBW6A-P1S
	White	LBW6A-P1W
	Yellow	LBW6A-P1Y
Square	Amber	LBW7A-P1A
oquare	Green	LBW7A-P1G
4	Red	LBW7A-P1R
	Blue	LBW7A-P1S
	White	LBW7A-P1W
	Yellow	LBW7A-P1Y

Dimensions


Panel Thickness: 0.5 to 3.2 mm Gasket Locking Ring Round * Solder/Tab Terminal LOCK 0.8W × 0.5t 2.8W × 0.5t Square 17.8

[Solder/Tab Terminal]

All dimensions in mm.

Terminal Arrangement (Bottom View)

[PC Board Terminal]





Pushbuttons

LBW1B-23T45*

Flush











Extended

Part No.

Square / Black Bezel

Switches & Pilot Devices

Square with Guard

Round only (metallic bezel available)

① Style	② Operation	③ Button Shape	Part No.	* Illumination Color Code
		Flush Round	LBW6B-M1T1@⑤	
	Momentary	Flush Square	LBW7B-M1T1@⑤	
Black bezel		Extended Round	LBW6B-M1T246	
ыаск регеі		Flush Round	LBW6B-A1T1@⑤	
	Maintained	Flush Square	LBW7B-A1T1@⑤	
		Extended Round	LBW6B-A1T2@⑤	Specify the color code in place
		Flush Round	LBW6MB-M1T1@⑤	of * in the Part No.
	Momentary	Flush Square	LBW7MB-M1T1@⑤	
Matallia hazal		Extended Round	LBW6MB-M1T2@⑤	B: black
Metallic bezel		Flush Round	LBW6MB-A1T1@⑤	G: green
	Maintained	Flush Square	LBW7MB-A1T1@⑤	R: red S: blue
		Extended Round	LBW6MB-A1T2@⑤	W: white
	Memontoni	Flush Round	LBW6GB-M1T1@⑤	Y: yellow
Guard Type	Momentary	Flush Square	LBW7GB-M1T1@⑤	
	Maintained	Flush Round	LBW6GB-A1T1@⑤	
	Maintained	Flush Square	LBW7GB-A1T1@⑤	

- The guard opens 180 degrees spring-return.
- PC board terminals available for gold contacts. To specify, see Part Number Interpretation below.
- Pushbuttons can be used with legend markings engraved on marking plates and lens buttons with clear film inserted in the lens is available. To specify, see Part Number Interpretation below. See for details on the marking plate and film.
- Extended pushbuttons available. To specify, see Part Number Interpretation below. Pushbuttons with guard is not available. Extended pushbuttons is available with momentary operation only.

Part Number Interpretation

LBW1B-23T45*



To be used for interpreting part numbers only, not for part number development.

① Style

-	
Code	Shape
6	Round / Black Bezel
7	Square / Black Bezel
6M	Round / Metallic Bezel
7M	Square / Metallic Bezel
6G	Round with Guard
7G	Square with Guard

© Operation				
Code	Operation			
Α	Maintained			
М	Momentary			

3 Operator Style

Code	Operation
1	Flush
2	Extended *

^{*} Extended style is available only for round (black/metallic bezel) and in momentary operation. Guard model is not available.

4 Contacts

Code	Contact	Code	Contact
1	Gold/SPDT	5	Silver/SPDT
2	Gold/DPDT	6	Silver/DPDT
3	Gold/3PDT	7	Silver/3PDT

5 Others

Code	Specification	Part No. Example
Blank	Solder/Tab Terminal	_
L (Note 1)	Lens	LBW6B-M1T1 <u>L</u> *
V	PC Board Terminal (Gold Contact Only)	LBW6B-M1T1 <u>V</u> *
VL (Note 1)	PC Board Terminal with Lens (Gold Contact Only)	LBW6B-M1T1 <u>VL</u> *

Note 1: Codes L and VL are available with flush operator only.

 Color code (*) for lens: A (amber), B (translucent lens with black nameplate), G (green), R (red), S (blue), W (white), Y (yellow) Relays & Sockets

Pushbuttons (Sub-assembled)

Contact Block	Operator	Button	Completed Unit
		. (-

Contact Block

Jointagt Brook				
Terminal Style		Material	Contact	Part Number
	Solder/Tab	Silver	SPDT	LB-T5
			DPDT	LB-T6
			3PDT	LB-T7
	or the same		SPDT	LB-T1V
	PCB	Gold	DPDT	LB-T2V
			3PDT	LB-T3V

Button

Style		Color	Part Number
		Black	LBW6A-B1B
		Green	LBW6A-B1G
	Round Flush	Red	LBW6A-B1R
	Houriu Husii	Blue	LBW6A-B1S
		White	LBW6A-B1W
		Yellow	LBW6A-B1Y
		Black	LBW6A-B2B
	Round (Extended)	Green	LBW6A-B2G
		Red	LBW6A-B2R
		Blue	LBW6A-B2S
		White	LBW6A-B2W
		Yellow	LBW6A-B2Y
1		Black	LBW7A-B1B
		Green	LBW7A-B1G
	Sauara Eluch	Red	LBW7A-B1R
	Square Flush	Blue	LBW7A-B1S
		White	LBW7A-B1W
		Yellow	LBW7A-B1Y


Operator

Style	Bezel Style	Shape	Momentary	Maintained
P	Black plastic	Round	LBW6L-M0	LBW6L-A0
	bezel	Square	LBW7L-M0	LBW7L-A0
		Round	LBW6ML-M0	LBW6ML-A0
2	Metallic bezel	Square	LBW7ML-M0	LBW7ML-A0
100-24	Plastic bezel with built-in switch guard	Round	LBW6GL-M0	LBW6GL-A0
		Square	LBW7GL-M0	LBW7GL-A0
	Flush Mount (Plastic)	Round (for	LBW6L-M20	LBW6L-A20
	Flush Mount (Metallic)	extended lens)	LBW6ML-M20	LBW6ML-A20



Dimensions All dimensions in mm.


Flush Pushbutton




Extended Pushbutton

[3PDT]


[3PDT]



Terminal Arrangement (Bottom View) SPDT/DPDT Contacts



3PDT Contacts



- For details on mounting hole layout, see 593.
- For details on pc board and circuit design, see 594.
- For details on single board mounting, see 593.

Selector Switches

LBW1S-2T34

Part No.









und / Black Bezel Squa

Square / Black Bezel

Round / Metalli

Square / Meta

- 0: 1	-0		③ Contact	Part No.		
① Style	② Operator Position			Gold Contact	Silver Contact	
		Maintained		SPDT	LBW①S-2T1	LBW①S-2T5
	90° 2-position	Walitalileu	L R	DPDT	LBW①S-2T2	LBW①S-2T6
			·	3PDT	LBW①S-2T3	LBW①S-2T7
Black bezel		Maintained	L C R	DPDT	LBW①S-3T2	LBW①S-3T6
	45°		\bigvee	3PDT	LBW①S-3T3	LBW①S-3T7
	3-position	Spring return two-way	DPDT	LBW①S-33T2	LBW①S-33T6	
			\bigvee	3PDT	LBW①S-33T3	LBW①S-33T7
	90° 2-position	Maintained L	L R	SPDT	LBW①S-2T1	LBW①S-2T5
				DPDT	LBW①S-2T2	LBW①S-2T6
			·	3PDT	LBW①S-2T3	LBW①S-2T7
Metallic bezel		Maintained L C R	L C R	DPDT	LBW①S-3T2	LBW①S-3T6
	45°		3PDT	LBW①S-3T3	LBW①S-3T7	
	3-position	Spring return two-way	DPDT	LBW①S-33T2	LBW①S-33T6	
			\vee	DPDT	LBW①S-33T3	LBW①S-33T7

- PC board terminals available for gold contacts. To specify, see Part Number Interpretation below.
- For contact operation, see 556.

Part Number Interpretation

LBW1S-2T34



To be used for interpreting part numbers only, not for part number development.

① Style

Code	Shape
6	Round / Black Bezel
7	Square / Black Bezel
6M	Round / Metallic Bezel
7M	Square / Metallic Bezel

② Operator Position

e operator i osition			
2-position	3-position		
Operator Position	Operator Position		
2 Maintained	3 Maintained	33 Spring return two-way	
L R	L C R	L C R	

③ Contacts

Code	Contact
1	Gold/SPDT (90° 2-position only)
2	Gold/DPDT
3	Gold/3PDT
5	Silver/SPDT (90° 2-position only)
6	Silver/DPDT
7	Silver/3PDT

4 Others

Code	Specification	Part No. Example
Blank	Solder/Tab Terminal	_
V	PC Board Terminal (Gold Contact Only)	LBW6S-2T1 <u>V</u>



Selector Switches (Sub-assembled)

Switches & Pilot Devices



Contact Block

Terminal Style		Material	Contact	Part Number
	Solder/Tab	Silver	SPDT	LB-T5
			DPDT	LB-T6
			3PDT	LB-T7
	PCB	Gold	SPDT	LB-T1V
			DPDT	LB-T2V
			3PDT	LB-T3V

SPDT contacts applicable for 2-position switches only.

Operator					
Style	Shape	Position	Function	Part Number	
Flush Mount (Plastic)	ъ	2	Maintained	LBW6S-2Y	
		3	Maintained	LBW6S-3Y	
	Round		Spring from both	LBW6S-33Y	
Round					
		2	Maintained	LBW7S-2Y	
	Square	3	Maintained	LBW7S-3Y	
Square	S		Spring from both	LBW7S-33Y	
Flush Mount		2	Maintained	LBW6MS-2Y	
(Metallic)	Round	3	Maintained	LBW6MS-3Y	
Round			Spring from both	LBW6MS-33Y	
		2	Maintained	LBW7MS-2Y	
10	Square	3	Maintained	LBW7MS-3Y	
Square	S		Spring from both	LBW7MS-33Y	

Key Selector Switches

LBW1K-23T45-6 Wave Key

Part No.









Disc Tumbler Key



	Round / Black B	Bezel Square / Blad	ck Bezel Round / Metallic	Bezel Squar	e / Metallic Bezel	Round /Metallic Bezel	Square / Metallic Bezel
① Style	② Operator Po	sition	⑤ Key Removable Pos	sition	⑤ Contact	Part No. Gold Contact	Silver Contact
			A: Key removable in all positions	SPDT	LBW①K-2ST1A	LBW®K-2ST5A	
Black bezel	90° 2-position	Maintained		L R	DPDT	LBW①K-2ST2A	LBW①K-2ST6A
	_ poortion				3PDT	LBW①K-2ST3A	LBW①K-2ST7A
	45°	Maintained	A: Key removable	Q [©] ®	DPDT	LBW①K-3ST2A	LBW①K-3ST6A
	3-position	Walliamoa	in all positions	$\overline{}$	3PDT	LBW①K-3ST3A	LBW①K-3ST7A
Metallic bezel	90° 2-position Maintained		SPDT	LBW①K-2ST1A	LBW①K-2ST5A		
		Maintained	A: Key removable in all positions	L R	DPDT	LBW①K-2ST2A	LBW①K-2ST6A
					3PDT	LBW①K-2ST3A	LBW①K-2ST7A
	45°	Maintained	A: Key removable	(L) (P) (R)	DPDT	LBW①K-3ST2A	LBW①K-3ST6A
	3-position	in all positions	3PDT	LBW①K-3ST3A	LBW①K-3ST7A		

- For operator position, see Part Number Interpretation below.
- For key removable position. see Part Number Interpretation below. The key cannot be removed in a spring returned position.
- · Two keys are supplied.
- Besides the standard key (key number 0H), six other keys are available.
- Disc tumbler keys also available. Only the standard key is available. To specify, see Part Number Interpretation below.
- PC board terminals available for gold contacts. To specify, see Part Number Interpretation below.
- For contact operation, see 593.

Part Number Interpretation

LBW1K-23T45-6



To be used for interpreting part numbers only, not for part number development.

① Style

Code	Shape
6	Round / Black Bezel
7	Square / Black Bezel
6M	Round / Metallic Bezel
7M	Square / Metallic Bezel

2 Operator Position

Code	Operator Position
2	90° 2-position maintained
3	45° 3-position maintained
33	45°-3-position spring return two-way

3 Key Style

Code	Key Style
S	Wave key
Blank	Disc tumbler key

4 Contacts

Code	Contact
1	Gold/SPDT (90° 2-position only)
2	Gold/DPDT
3	Gold/3PDT
5	Silver/SPDT (90° 2-position only)
6	Silver/DPDT
7	Silver/3PDT

6 Key Number (for wave keys only)

Code	
0H or Blank	Standard key
1H to 2H	Reversible key
3H to 6H	Non-reversible key

(5) Key Removal Position

2-position				
Key Removable Position				
A: Key removable in all positions	B : Key removable at left position only			
(L) (R)	© 8			

Others

Code	Specification	Part No. Example
Blank	Solder/Tab Terminal	_
٧	PC Board Terminal (Gold Contact Only)	LBW6K-2T1 <u>V</u> A

n
5 17
D: Key removable at center only

3-position

Spring return two-way



• Key removable at ①, ©, ®. Key retained at **O**, **O**.



Key Selector Switches (Sub-assembled)

Contact Block Operator Completed Unit







Contact Block

Terminal Style		Material	Contact	Part Number
Solder/Tab		Silver	SPDT	LB-T5
			DPDT	LB-T6
			3PDT	LB-T7
PCB		Gold	SPDT	LB-T1V
			DPDT	LB-T2V
			3PDT	LB-T3V


Operator

Style	Shape	Position	Function	Key Style	Key Remove Position	Part number
Black Plastic				Disc	All positions	LBW6K-2A
bezel		2	90° 2-position	tumbler key	Left	LBW6K-2B
		_ Z	maintained		All positions	LBW6K-2SA
				Wave key	Left	LBW6K-2SB
10000			45° 3-position	Disc	All positions	LBW6K-3A
	Round		maintained	tumbler key	Center	LBW6K-3D
				Wave	All positions	LBW6K-3SA
		3		key	Center	LBW6K-3SD
		3	45°-3-position spring return two-way	Disc tumbler key	All positions	LBW6K-33D
				Wave key	Center	LBW6K-33SD
		2	90° 2-position maintained	Disc tumbler key	All positions	LBW7K-2A
					Left	LBW7K-2B
				Wave key	All positions	LBW7K-2SA
					Left	LBW7K-2SB
			45° 3-position	Disc tumbler key	All positions	LBW7K-3A
	Square		maintained		Center	LBW7K-3D
				Wave	All positions	LBW7K-3SA
		3		key	Center	LBW7K-3SD
			45°-3-position spring return two-way	Disc tumbler key	Center	LBW7K-33D
			,	Wave key		LBW7K-33SD


Style	Shape	Position	Function	Key Style	Key Remove Position	Part number
Metallic Bezel	Bezel 90° 2-position Disc		Disc tumbler	All positions	LBW6MK-2A	
-			maintained	key	Left	LBW6MK-2B
0		2		Wave key	All positions	LBW6MK- 2SA
					Left	LBW6MK- 2SB
			45° 3-position maintained	Disc	All positions	LBW6MK-3A
	Round		maintaineu	tumbler key	Center	LBW6MK-3D
				Wave key	All positions	LBW6MK- 3SA
		3			Center	LBW6MK- 3SD
			45°-3-position spring return two-way	Disc tumbler key	Center	LBW6MK- 33D
				Wave key		LBW6MK- 33SD
		2	90° 2-position maintained	Disc tumbler key	All positions	LBW7MK-2A
					Left	LBW7MK-2B
				Wave key	All positions	LBW7MK- 2SA
					Left	LBW7MK- 2SB
			45° 3-position maintained	Disc	All positions	LBW7MK-3A
	Square		mamtameu	tumbler key	Center	LBW7MK-3D
				Wave key	All positions	LBW7MK- 3SA
		3			Center	LBW7MK- 3SD
			45°-3-position spring return two-way	Disc tumbler key	Center	LBW7MK- 33D
				Wave key		LBW7MK- 33SD

Dimensions All dimensions in mm.


Key Selector Switches with Wave Key




Key Selector Switches with Disc Tumbler Key



Terminal Arrangement (Bottom View) SPDT/DPDT Contacts



3PDT Contacts



- For details on mounting hole layout, see 593.
- For details on pc board and circuit design,
- For details on single board mounting, see 593.



[3PDT]

Contact Operation


Switches & Pilot Devices

Selector Switch, Illuminated Selector Switch, Key Selector Switch


Operator Position & Contact Operation (Top View)								
		Position		Contact		† Center	✓ Right	
	L R		R	SPDT	NO1 NC1		NOT NCT	
90° 2-position	Main	tained	Spring retur	n from right	DPDT	Left Right NO1 NC1 NO2 NC2 C1 C2		Left Right NO1 NC1 NO2 NC2 C1 C2
					3PDT	Left Center Right NO1NC1NO2NC2NO3NC3		Left Center Right NO1 NC1 NO2NC2 NO3 NC3
45°	. C -	C	C		DPDT	Left Right NO1 NC1 NO2 NC2	Left Right NO1 NC1 NO2 NC2	Left Right NO1NC1 NO2NC2
3-position	Maintained	Spring return from right	Spring return from left	Spring return two- way	3PDT	Left Center Right NO1NC1 NO2NC2 NO3NC3	Left Center Right NO1NC1 NO2NC2 NO3NC3 C1 C2 C3	Left Center Right NO1NC1 NO2NC2 NO3NC3

Mounting Hole Layout (mm)

LBW Series Flush Bezel (LBW6/LBW6M/LBW6G)




LBW Series Flush Bezel LBW6/LBW6M/LBW6G




* 53 mm minimum for switches with guard

LBW Series Flush Bezela LBW7/LBW7M/LBW7G



Single Board Mounting

IDEC's LBW Series is available for single board mounting.



Installing and Removing Contact Blocks

Turn the locking lever to install and remove contact blocks on the PC using a screwdriver from a hole in the PC board. See "Notes for Designing PC Board and Circuit" on 594. Determine the location of the switches so that the locking lever can be operated. See "Removing and Installing the Contact Block" on 598.

Mounting Holes and Assembly Procedure

Drill mounting holes in the panel as shown below. When the units are mounted collectively, provide adequate clearance.

Assembly Procedure

- Install the operator to the panel.
- 2. Mount the contact block to the operator from the rear.
- 3. Turn the locking lever to lock the contact block.
- 4. Insert the PC board to terminals and solder.
- Note 1: Make sure that each terminal is inserted into the PC board correctly.
- Note 2: Do not apply tensile force to the connector cable for an extended period of time.
- Note 3: Do not expose the contact block to water.
- Note 4: Ensure to lock contact blocks when the contact blocks are installed on the operators.


UP series can be installed on the same board. For details, see 599

Notes for Designing PC Board and Circuit


All dimensions in mm.

- Use 1.6-mm-thick glass epoxy PC board with drilled holes.
- Design a circuit so that the LBW series can operate within the rated voltage and current range. Make sure that inrush current and voltage do not exceed the rating.
- Minimum applicable load is 5V AC/DC, 1 mA on gold contacts. Applicable range is subject to the operating condition and load.
- Since the *2.8-mm-wide terminal touches the PC board as shown on the right, short circuit may occur with pattern lines. Design a circuit that prevents short circuits.


SPDT/DPDT Contacts




3PDT Contacts



PC Board Drilling Layout (Bottom View) SPDT/DPDT Contacts



3PDT Contacts



- Note 1: When designing, note the alignment of center lines of the contact blocks and center lines of the operators.
- Note 2: The diameter of the terminal hole is ø1.2.
- Note 3: Hole diameter may vary to meet installation requirements. Determine the location and the size of the hole so that the locking lever can be operated.

Accessories

Switches & Pilot Devices

Sha	pe		Specification	Part No.	Remarks
Lock	Locking Ring Wrench		Metal (Nickel-plated brass)	MT-001	Used to tighten the locking ring when installing the units on to the panel.
For Standard Bezels	Lens Removal Tool 60.0		Stainless Steel	MT-101	Used to remove the lens or button. (for standard bezels)
	Mounting Hole Plug ①	1. For round units (LBW6/LBW6M)	[Plug] Polyamide (Black) [Gasket]	LBW9Z-BS6*	* Color code: blank (black), W (white) Degree of protection: IP65
	2	2. For square units (LBW7/LBW7M)	Nitrile rubber [Mounting Plate] Stainless Steel	LBW9Z-BS7*	Panel thickness: 0.5 to 3.2 mm See 596 for dimensions.
sh Bezels	Mounting Hole Plug	Metal	[Plug] Zinc diecast [Locking Ring] Polyamide [Gasket] Nitrile rubber	LW9Z-BM	Degree of protection: IP66 Tightening torque: 1.2 N·m See 596 for dimensions.
For LBW Series Flush Bezels	Mounting Hole Plug	Rubber	Nitrile rubber	LW9Z-BP1	Degree of protection: IP65 Tightening torque: 2.0 N·m See 596 for dimensions.
	ninal Cover ① ②	1. For SPDT/DPDT contacts	PBT	LB9Z-VL2	See 596 for dimensions.
	2. For 3PDT contacts		(White)	LB9Z-VL3	See 598 for mounting.
Reversible key For key selector switches (wave key) Non-reversible key		Metal (zinc nickel-plated)	LA9Z-SK-*	Specify a key number in place of * in the Part No. Blank: Standard key 0H (reversible) 1H to 2H: Reversible key 3H to 6H: Non-reversible key See 596 for dimensions.	
Key	s 🍶	For key selector switches (disc tumbler key)	Metal (brass nickel-plated) 18×1.8×25.1 t1.8	AS6-SK-132	

596

Accessories

Shape		Material / Dimensions (W×H×D)	Part No.	Remarks	
	Lens	1. For round flush units	Polyarylate ø20 H4	HA9Z-L11*	Specify the color code in place of * in the part no. A: Amber, C: Clear, G: Green, R: Red,
	2	2. For square flush units	Polyarylate ø20 H4	HA9Z-L21*	S: Blue, Y: Yellow Note: Use a clear lens for pure white (PW) illumination.
	3	3. For round extended units	Polyarylate ø20.2 H7.8	LBW9Z-L12*	Specify the color code in place of * in the part no. A: Amber, G: Green, R: Red, S: Blue, W: clear, Y: Yellow Note: Use a clear lens for pure white (PW) illumination.
	Buttons ①	1. For round flush units	Polyacetal ø20 H3.2 (L5)	HA9Z-B11*	
	3	2. For square flush units	Polyacetal ø20 H3.9 (L5)	HA9Z-B21*	Specify the color code in place of ∗ in the part no. B: Black, G: Green, R: Red, S: Blue W: White, Y: Yellow
		3. For round extended units	Polyacetal ø19.8 H7.3 (L9.1)	HA9Z-B12*	w. wille, i. reliew
	Marking plate	1. For round flush units	Acrylic ø17 t0.85 (L1.1)	HA9Z-P1*	
		2. For square units	Acrylic □18.4 t0.85	HA9Z-P2*	Specify the color code in place of * in the part no. B: Black, W: White
		3. For extended units	Acrylic ø15 t3.0	LBW9Z-P12W	
LBW Series	Anti-rotation Ring	LBW series	Metal (Stainless steel) 25×8.2×24.8 t0.8	LBW9Z-LP6	
Lo	cking ring	All models	Polyamide ø17.9 H3.9	LB9Z-LN	

Dimensions for Accessories

For round units (LBW9Z-BS6*)



Mounting Hole Layout




For round units (LBW9Z-BS6*)



Mounting Hole Layout




All dimensions in mm.




Terminal Cover


For SPDT/DPDT contacts (LB9Z-VL2)




For 3PDT contacts (LB9Z-VL3)



Key (Wave Key) Reversible key



Non-reversible key





Maintenance Parts

Switches & Pilot Devices

Maintenance LED Unit Package Quantity: 1

Shape	Rated Operating Voltage	Part No. (Ordering No.)	* Color Code
LED Unit	5V DC	LB9Z-LED5*	A: Amber G: Green
- PARECULA (12V AC/DC	LB9Z-LED1*	PW: Pure White R: Red
	24V AC/DC	LB9Z-LED2*	S: Blue W: White

• Use a pure white (PW) LED unit for yellow (Y) illumination.

Transformer

Package Quantity: 1

Transformer	Primary Voltage	Secondary Voltage	Part No. (Ordering No.)	Applicable Load
For 24V	100/110V AC	100/110V AC ±10%	TWR512	
· · · · ·	200/220V AC	200/220V AC ±10%	TWR522	LB9Z-LED2* (24V AC/DC LED unit)
The same	400/440V AC	400/440V AC±10%	TWR542	, ,


- Terminal cover (TWR-VL3) is supplied as standard.
- Connect one LB9Z-LED2* to a transformer.

Specifications

Part No.	TWR5□2
Operating Voltage	100/110V AC, 200/220V AC, 400/440V AC (50/60Hz)
Current Draw	2.4VA
Rated Insulation Voltage	600V
Insulation Resistance	100 MΩ minimum (500V DC megger)
Operating Temperature	−30 to +60°C (no freezing)
Storage Temperature	-40 to +80°C (no freezing)
Operating Humidity	35 to 85% RH (no condensation)
Vibration Resistance	Damage Limits: 30 Hz, amplitude 1.5 mm
The faction modification	Operating extremes: 5 to 55 Hz, amplitude 0.5 mm
Shock Resistance	Damage limits: 1,000 m/s ²
OHOCK HESISTANCE	Operating Extremes: 100 m/s ²
Dielectric Strength	2,500V AC, 1 minute
Terminal Screw	M3.5
Applicable Wire	2 mm² maximum, 2 wires maximum
Weight (approx.)	87g

Dimensions

All dimensions in mm.



• Use end clip BC9Z-E/N35NPN10 when using 400/440V AC primar y voltage transformers.

Precautions & Instructions Safety Precautions

- Turn off the power to the LBW series control units before installation, removal, wiring, maintenance, and inspection. Failure to turn power off may cause electrical shocks or fire hazard.
- To avoid burning your hand, use the lamp holder tool when replacing the lamps.

For wiring, use wires of a proper size to meet voltage and current requirements.
 Solder correctly according to the instructions in "Wiring" and "Notes on Terminal Cover." Improper soldering may cause overheating and create a fire hazard. Also, when using tab terminals, use receptacles of appropriate size.

Instructions

Wiring

- Solder the terminals at 350°C within 3 seconds using a 60W soldering iron. Sn-Ag-Cu type is recommended. When soldering, do not touch the LB series with the soldering iron. Also ensure that no tensile force is applied to the terminals. Do not bend the terminal or apply excessive force to the terminal.
- 2. Use non-corrosive liquid flux.


Terminal Cover

Solder/tab terminal


Insert the terminal cover into the contact block with the TOP markings on the contact block and the terminal cover in the same direction.

Note: When wiring, insert the lead wires into the terminal cover holes before soldering. After wiring, terminal covers cannot be installed.

Standard Bezel



Flush Bezel



Operating Environment

- Do not use the LB series where corrosive gases exist or under an environment exceeding the operating temperature and humidity ranges.
 Otherwise, damage such as contact failure or change of the surface color may occur.
- Major parts of the switch are plastic. Scratches or damage may occur
 when scraped with a sharp object or if excessive load or shock is applied.
 Note that this may cause operation and appearance failure of the operator
 and bezel
- Application of detergent, cutting oil, or special chemicals to the switch may result in operation and/or appearance failure such as a change in surface color.


Handling

Contacts (micro switch)

When using NC (normally closed) and NO (normally open) contacts of the same microswitch, avoid connections of different voltages, or connections of different types of power supplies. Failure to observe this instruction may cause a short-circuit.

Removing and Installing the Contact Block

- 3. Turn the locking lever on the contact block in the direction opposite to the arrow on the housing. Then the contact block can be removed.
- 4. Insert the contact block with the TOP markings on the contact block and the operator placed in the same direction. Then lock the units, turning the locking lever in the direction of the arrow.




Panel Mounting

Remove the contact block from the operator. Insert the operator into the panel cut-out from the front, then install the contact block to the operator.

locking lever

Flush Bezel



Notes on Mounting

Use the optional ring wrench (MT-001) to mount the operator onto the panel. Tightening torque should not exceed 0.7 N·m. Do not use pliers. Excessive tightening will damage the locking ring.



Mounts on the same panel as LB/LBW series

• Three illumination colors: Green (G), red (R), and white (W)

Specifications

opoomoun	00		
Color Code		Red (R), White (W)	G (Green)
Rated Current (I)		7mA	2mA
Maximum Current (Ta: 25°C)	Reverse Voltage (V _R)	9V	5V
	Operating Temperature (T _{opr})	−25 to +55°C (no freezing)	
	Storage Temperature (T _{stg})	−30 to +80°C (no freezing)	
Forward Voltage (V _f)		Standard value: 2V (If=7mA)	Standard value: 2.7V (If=2 mA)
Dielectric Voltage		Between live and dead parts: 500V AC, 1 minute	
Weight (approx.)		4.3g (UP8-89V1), 5.1g (UP8-89V2)	



UP Series

	Mounting Hole Size	Shape	Degree of Protection (IEC 60529)	Matching LB/ LBW Mounting Style	Part No.	Illumination Color Code
ø8 UP8	UP8 With standard bezel		oud IP40	Standard Bezel	UP8-89V1*	Specify the color code in place of * in the Part No.
With flush bezel		Shroud		Flush Bezel	UP8-89V2*	
ø9 UP9P	di la	Shroud	IP65	Standard bezel Flush bezel	UP9P-99V1*	R: red W: white

• LED cannot be replaced.


Note: Connect an external current limiting resistor in series. Otherwise, the LED may be damaged.


Dimensions All dimensions in mm.

M8×P0.75

12








Panel Thickness 0.6 to 6



UP8-89V2

[Assembly Drawing]



Dimensions (L)

Standard Bezel	22.5mm
Flush Bezel	29.9mm

PC Board Mounting Hole



Panel Cut-out UP8

O





UP9P

Panel Thickness 0.6 to 4 UP9P-99V1

Internal Circuit



The longer pin is the positive terminal

Safety Precautions

 Turn off power to the unit before installation, removal, wiring, maintenance, and inspection.


Failure to turn off may cause electrical shocks or fire hazard.

- For wiring, use wires of a proper size to meet the voltage and current requirements.
- Improper soldering or failure to tighten the terminal screw may cause overheating and fire.


Single Board Mounting

UP series miniature pilot light single board mounting types can be mounted with LB/ LBW series on the same panel.

Follow the instructions below on single board mounting.




1. Mount the LED kit to the PC board.




Temporary mounting


- 1. Note the polarity of the terminals and insert the terminals to the PC board.
- Make sure that part A of the LED kit is pressed tightly to the PC board. Bend the terminals sideways as shown on the left.
- 2. Mount the operator and the UP series pilot lights on to the control panel.



3. Mount the contact block to the operator of the miniature control unit and lock the unit by turning the locking lever.



4. Install the PC board in 1. to the panel in 3.



* When mounting LB/LBW and UP series on a single board, make sure that the distance between the front of the panel and the mounting side of the PC board (gasket distortion is taken into consideration) is as shown in the table below.

Part No.	Mountable Unit	Distance (*)
UP8-89V1*	Standard bezel	22.5mm
UP8-89V2*	Flush bezel	29.9mm
UP9P-99V1*	Standard bezel	22.5mm
UF3F-33V1*	Flush bezel	29.9mm

5. Solder the terminals.

Before soldering, make sure that each terminal of the contact block is securely inserted into the PC board holes.


Instructions

Polarity

Pay attention to the polarity of the power supply as UP series units do not contain a diode for protection against reverse polarity. The long terminal is positive and the short terminal is negative.

Current Limiting Resistor

When using a UP series unit without a built-in current limiting resistor, connect an external current limiting resistor. Calculate the resistance using the following formula.



Resistance (Ω)=

Operating Voltage (V) – Forward Voltage (Vf)

Rated Current (I) *

* Rated Current (I) = R (red), W (white) : 0.007A G (green) : 0.002A

Forward Voltage (Vf) = R (red), W (white) : 2V G (green) : 2.7V

Note: Use a resistor of higher resistance than the calculated value (Ω)

Rated Wattage of Resistor (W) = Rated Current \times Operating Voltage \times 2 to 3 *

* 2 to 3 is a safety factor

<Current Limiting Resistor Reference Value>

Color Operating Voltage	Red (R), White (W)	Green (G)
5V DC	430Ω (1/4W)	1200Ω (1/4W)
6V DC	560Ω (1/4W)	1600Ω (1/4W)
12V DC	1500Ω (1/4W)	4700Ω (1/4W)
24V DC	3000Ω (1/2W)	11000Ω (1/4W)

Wiring

Solder the terminal at 350°C within 3 seconds using a 60W soldering iron. SnAgCu type lead-free solder is recommended.


When soldering, do not touch the pilot light housing with the terminal. Do not bend the terminal or apply excessive force to the terminal.

Notes on Panel Mounting

Tightening torque should not exceed 0.49 N·m. Do not use pliers. Do not tighten with excessive force, otherwise the locking ring will be damaged.

PC Board and Circuit Design

Use glass epoxy copper clad laminate, double-sided through-hole PC boards with a thickness of 1.6 mm.



Example of single board mounting

