


ST3485EB, ST3485EC

3.3 V powered, 15 kV ESD protected, up to 12 Mbps RS-485/ RS-422 transceiver

Datasheet - production data



Features

- ESD protection
 - ±15 kV IEC 61000-4-2 air discharge
 - ±8 kV IEC 61000-4-2 contact discharge
- Operate from a single 3.3 V supply no charge pump required
- Interoperable with 5 V logic
- 1 µA low current shutdown mode max.
- Guaranteed 12 Mbps data rate
- -7 to 12 V common mode input voltage range
- Half duplex versions available

- Industry standard 75176 pinout
- Current limiting and thermal shutdown for driver overload protection
- Guaranteed high receiver output state for floating inputs with no signal present
- Allow up to 64 transceivers on the bus
- Available in SO-8 package

Description

The ST3485EB/EC device is ±15 kV ESD protected, 3.3 V low power transceiver for RS-485 and RS-422 communications. The device contains one driver and one receiver in half duplex configuration.

The ST3485E device transmits and receives at a guaranteed data rate of at least 12 Mbps.

All transmitter outputs and receiver inputs are protected to ±15 kV IEC 61000-4-2 air discharge.

Driver is short-circuit current limited and is protected against excessive power dissipation by thermal shutdown circuitry that places the driver outputs into a high impedance state.

Table 1. Device summary

Order code	Temperature range	Package	Packaging
ST3485ECDR	0 to 70 °C	SO-8 (tape and reel)	2500 parts per reel
ST3485EBDR	-40 to 85 °C	SO-8 (tape and reel)	2500 parts per reel

Contents

1	Pin configuration	}
2	Truth tables4	Ļ
3	Maximum ratings	5
4	Electrical characteristics 6	>
5	Test circuits and typical characteristics9)
6	Package information	,
7	Revision history)

ST3485EB, ST3485EC Pin configuration

1 Pin configuration

Figure 1. Pin connections




Table 2. Pin description

Pin n°	Symbol	Name and function
1	RO	Receiver output. If A > B by 200 mV, RO will be high; if A < B by 200 mV, RO will be low.
2	RE	Receiver output enable. RO is enabled when \overline{RE} is low; RO is high impedance when \overline{RE} is high. If \overline{RE} is high and DE is low, the device will enter a low power shutdown mode.
3	DE	Driver output enable. The driver outputs are enabled by bringing DE high. They are high impedance when DE is low. If \overline{RE} is high DE is low, the device will enter a low-power shutdown mode. If the driver outputs are enabled, the part functions as line driver, while they are high impedance, it functions as line receivers if \overline{RE} is low.
4	DI	Driver input. A low on DI forces output A low and output B high. Similarly, a high on DI forces output A high and output B low.
5	GND	Ground
6	Α	Non-inverting receiver input and non-inverting driver output.
7	В	Inverting receiver input and inverting driver output.
8	V _{CC}	Supply voltage: V _{CC} = 3 V to 3.6 V.

2 Truth tables

Table 3. Truth table (driver)

Inputs			Out	puts	Mode
RE	DE	DI	В	Α	Wode
Х	Н	Н	L	Н	Normal
X	Н	L	Н	L	Normal
L	L	Х	Z	Z	Normal
Н	L	Х	Z	Z	Shutdown

Note: X = "don't care"; Z = high impedance.

Table 4. Truth table (receiver)

	Inputs		Output	Modo
RE	DE	A-B	RO	Mode
L	L	≥ 0.2 V	Н	Normal
L	L	≤ -0.2 V	L	Normal
L	L	Inputs open	Н	Normal
Н	L	X	Z	Shutdown

Note: X = "don't care"; Z = high impedance.

ST3485EB, ST3485EC Maximum ratings

3 Maximum ratings

Table 5. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V _{CC}	Supply voltage	7	V
V _I	Control input voltage (RE, DE)	-0.3 to 7	V
V _{DI}	Driver input voltage (DI)	-0.3 to 7	٧
V _{DO}	Driver output voltage (A, B)	±14	V
V _{RI}	Receiver input voltage (A, B)	±14	V
V _{RO}	Receiver output voltage (RO)	-0.3 to (V _{CC} + 0.3)	٧

Note:

Absolute maximum ratings are those values beyond which damage to the device may occur. Functional operation under these condition is not implied.

Table 6. ESD performance: transmitter outputs, receiver inputs (A, B)

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
ESD	ESD protection voltage	IEC 61000-4-2 air discharge		±15		kV
ESD	ESD protection voltage	IEC 61000-4-2 contact discharge		±8		kV

4 Electrical characteristics

Table 7. Electrical characteristics (V_{CC} = 3 V to 3.6 V, T_A = -40 to 85 °C, unless otherwise specified. Typical values are referred to T_A = 25 °C)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I _{SUPPLY}	V _{CC} Power supply current	Natard DL 0 V an V	$\frac{DE}{RE} = V_{CC},$ $RE = 0 \text{ V or } V_{CC}$		1.3	2.2	mA
		No load, DI = 0 v oi v _{CC}	<u>DE</u> = 0 V, RE = 0 V		1.2	1.9	mA
I _{SHDN}	Shutdown supply current	DE = 0 V, \overline{RE} = V _{CC} , DI = 0 V or V _{CC}			0.002	1	μA

Table 8. Logic input electrical characteristics (V_{CC} = 3 V to 3.6 V, T_A = -40 to 85 °C, unless otherwise specified. Typical values are referred to T_A = 25 °C)

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
V_{IL}	Input logic threshold low	DE, DI, RE			1.3	0.8	V
V _{IH}	Input logic threshold high	DE, DI, RE					V
I _{IN1}	Logic input current	DE, DI, RE				±2.0	μA
	Input current (A, B)	DE = 0 V, V _{CC} = 0 or 3.6 V	V _{IN} = 12 V			1	mA
I _{IN2}	input current (A, B)	DE - 0 v, v _{CC} - 0 01 3.6 v	V _{IN} = -7 V			-0.8	mA

Table 9. Transmitter electrical characteristics (V_{CC} = 3 V to 3.6 V, T_A = -40 to 85 °C, unless otherwise specified. Typical values are referred to T_A = 25 °C)

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
		R _L = 100 Ω (RS-422) (<i>Figure 2</i>)	2			V
V_{OD}	Differential drive output	R _L = 54 Ω (RS-485) (<i>Figure 2</i>)	1.5			V
		R _L = 60 Ω (RS-485) (<i>Figure 3</i>)	1.5			V
ΔV _{OD}	Change in magnitude of driver differential output voltage for complementary output states ⁽¹⁾	R _L = 54 Ω or 100 Ω (<i>Figure 2</i>)			0.2	V
V _{OC}	Driver common mode output voltage	R _L = 54 Ω or 100 Ω (<i>Figure 2</i>)			3	V
ΔV _{OC}	Change in magnitude of driver common mode output voltage ⁽¹⁾	R _L = 54 Ω or 100 Ω (<i>Figure 2</i>)			0.2	V
I _{OSD}	Driver short-circuit output current				±250	mA

^{1.} ΔV_{OD} and ΔV_{OC} are the changes in V_{OD} and V_{OC} , respectively, when the DI input changes state.

6/21 DocID9102 Rev 6

Table 10. Receiver electrical characteristics (V_{CC} = 3 V to 3.6 V, T_A = -40 to 85 °C, unless otherwise specified. Typical values are referred to T_A = 25 °C)

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
V _{TH}	Receiver differential threshold voltage	V _{CM} = -7 V to 12 V, DE = 0	-0.2		0.2	V
ΔV_{TH}	Receiver input hysteresis	V _{CM} = 0 V		70		mV
V _{OH}	Receiver output high voltage	I _{OUT} = -4 mA, V _{ID} = 200 mV (<i>Figure 4</i>)	2			V
V _{OL}	Receiver output low voltage	I _{OUT} = 4 mA, V _{ID} = -200 mV, (<i>Figure 4</i>)			0.4	V
I _{OZR}	3-state (high impedance) output current at receiver	$V_{CC} = 3.6 \text{ V}, V_{O} = 0 \text{ V to } V_{CC}$			±1	μA
R _{RIN}	Receiver input resistance	V _{CM} = -7 V to 12 V	24			kΩ
I _{OSR}	Receiver short-circuit current	V _{RO} = 0 V to V _{CC}	7		60	mA

Table 11. Driver switching characteristics (V_{CC} = 3 V to 3.6 V, T_A = -40 to 85 °C, unless otherwise specified. Typical values are referred to T_A = 25 °C)

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
D_R	Maximum data rate		12	15		Mbps
t _{DD}	Differential output delay	R_L = 60 Ω , C_L = 15 pF, (<i>Figure 5</i> and <i>Figure 6</i>)		18	30	ns
t _{TD}	Differential output transition time	R_L = 60 Ω , C_L = 15 pF, (<i>Figure 5</i> and <i>Figure 6</i>)		12	20	ns
t _{PLH} t _{PHL}	Propagation delay	R_L = 27 Ω , C_L = 15 pF, (<i>Figure 9</i> and <i>Figure 10</i>)		18	30	ns
t _{PDS}	t _{PLH -} t _{PHL} driver propagation delay skew ⁽¹⁾	R_L = 27 Ω , C_L = 15 pF, (<i>Figure</i> 9 and <i>Figure</i> 10)		2	5	ns
t _{PZL}	Output enable time	R_L = 110 Ω, (<i>Figure 11</i> and <i>Figure 12</i>)		19	35	ns
t _{PZH}	Output enable time	R_L = 110 $Ω$, (<i>Figure 7</i> and <i>Figure 8</i>)		30	50	ns
t _{PHZ}	Output disable time	R_L = 110 Ω, (<i>Figure 7</i> and <i>Figure 8</i>)		19	35	ns
t _{PLZ}	Output disable time	R_L = 110 Ω, (<i>Figure 11</i> and <i>Figure 12</i>)		30	50	ns
t _{SKEW}	Differential output delay skew			1	3	ns
t _{PSH}	Driver enable from shutdown to output high	R_L = 110 Ω (<i>Figure 7</i> and <i>Figure 8</i>)		30	50	ns
t _{PSL}	Driver enable from shutdown to output low	R_L = 110 Ω (<i>Figure 11</i> and <i>Figure 12</i>)		19	35	ns

^{1.} Measured on $|t_{PLH}(A)-t_{PHL}(A)|$ and $|t_{PLH}(B)-t_{PHL}(B)|$.

Table 12. Receiver switching characteristics (V_{CC} = 3 V to 3.6 V, T_A = -40 to 85 °C, unless otherwise specified. Typical values are referred to T_A = 25 °C)

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
t _{RPLH}	Propagation delay	V _{ID} = 0 V to 3 V, C _L = 15 pF (<i>Figure 13</i> and <i>Figure 14</i>)		30	50	ns
t _{RPDS}	t _{RPLH} - t _{RPHL} receiver propagation delay skew	V _{ID} = 0 V to 3 V, C _L = 15 pF (<i>Figure 13</i> and <i>Figure 14</i>)		1	3	ns
t _{PRZL}	Receiver output enable time to low level	C _L = 15 pF, (<i>Figure 15</i> and <i>Figure 17</i>)		10	20	ns
t _{PRZH}	Receiver output enable time to high level	C _L = 15 pF, (<i>Figure 15</i> and <i>Figure 16</i>)		10	20	ns
t _{PRHZ}	Receiver output disable time from high level	C _L = 15 pF, (<i>Figure 15</i> and <i>Figure 18</i>)		10	20	ns
t _{PRLZ}	Receiver output disable time from low level	C _L = 15 pF, (<i>Figure 15</i> and <i>Figure 19</i>)		10	20	ns
t _{PRSH}	Receiver output enable time from shutdown to high level	C _L = 15 pF, (<i>Figure 15</i> and <i>Figure 16</i>)		10	20	ns
t _{PRSL}	Receiver output enable time from shutdown to low level	C _L = 15 pF, (<i>Figure 15</i> and <i>Figure 17</i>)		20	40	μs

Note:

- 1. ΔV_{OD} and ΔV_{OC} are the changes in V_{OD} and V_{OC} , respectively, when the DI input changes state.
- 2. Measured on $|t_{PLH}(A) t_{PHL}(A)|$ and $|t_{PLH}(B) t_{PHL}(B)|$.
- 3. The transceivers are put into shutdown by bring \overline{RE} high and DE low. If the input are in state for less than 80 ns, the part are guaranteed not to enter shutdown. If the inputs are in this state for at least 300 ns, the parts are guaranteed to have entered shutdown.

5 Test circuits and typical characteristics

Figure 2. Driver and V_{OC} test load




Figure 3. Driver V_{OD} with varying common mode voltage test load





Figure 4. Receiver \mathbf{V}_{OH} and \mathbf{V}_{OL} test circuit




IN(1)CS10910V1


Figure 5. Drive differential output delay transition time test circuit

- The input pulse is supplied by a generator with the following characteristics: PRR = 250 kHz, 50% duty cycle, $t_r \le 6.0$ ns, $Z_O = 50~\Omega$.
- 2. C_L includes probe and stray capacitance.

3 V IN 1.5 V 0 V 90% 90% OUT 50% 50% 10% 10% CS10820V1

Figure 6. Drive differential output delay transition time waveform





- 1. The input pulse is supplied by a generator with the following characteristics: PRR = 250 kHz, 50% duty cycle, $t_r \le 6.0$ ns.
- 2. $\,$ C $_{L}$ includes probe and stray capacitance.




Figure 8. Drive enable and disable times waveforms

1. t_{PZH} is valid if the driver is initially disabled (\overline{RE} is high), t_{PSH} is valid if the driver is initially in shutdown mode (\overline{RE} is low).




Figure 9. Drive propagation time test circuit

- 1. The input pulse is supplied by a generator with the following characteristics: PRR = 250 kHz, 50% duty cycle, $t_r \le 6.0$ ns.
- 2. C_L includes probe and stray capacitance.





Figure 10. Drive propagation time waveform

Figure 11. Drive enable and disable times test circuit



- 1. The input pulse is supplied by a generator with the following characteristics: PRR = 250 kHz, 50% duty cycle, $t_r \le 6.0$ ns.
- 2. C_L includes probe and stray capacitance.




Figure 12. Drive enable and disable times waveforms

1. t_{PZL} is valid if the driver is initially disabled (\overline{RE} is high), t_{PSL} is valid if the driver is initially in shutdown mode (\overline{RE} is low).

 $IN^{(1)}$ _ OUT $\stackrel{=}{\Box}$ C_L= 15 pF⁽²⁾

Figure 13. Receiver propagation delay time test circuit

- 1. The input pulse is supplied by a generator with the following characteristics: PRR = 250 kHz, 50% duty cycle, $t_r \le 6.0$ ns.
- 2. C_L includes probe and stray capacitance.




Figure 14. Receiver propagation delay time waveforms






Figure 15. Receiver enable and disable times test circuit

- The input pulse is supplied by a generator with the following characteristics: PRR = 250 kHz, 50% duty cycle, $t_r \le 6.0$ ns.
- 2. C_L includes probe and stray capacitance.

3 V S1 OPEN IN S2 CLOSED S3 = 1.5 V0 V †_{PRZH} †_{PRSH} V_{OH} OUT 1.5 V CS10870

Figure 16. Receiver enable and disable times waveform








IN $\begin{array}{c}
1.5 \text{ V} \\
\hline
S1 \text{ OPEN} \\
S2 \text{ CLOSED} \\
S3 = 1.5 \text{ V}
\end{array}$ OV $\begin{array}{c}
0 \text{ V}
\end{array}$ OUT $\begin{array}{c}
0 \text{ V}
\end{array}$ CS10890


Figure 18. Receiver enable and disable times waveform


Figure 19. Receiver enable and disable times waveform

















6 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.






Figure 27. SO-8 package outline

Table 13. SO-8 package mechanical data

	Dimensions							
Symbol	mm			inch				
	Min.	Тур.	Max.	Min.	Тур.	Max.		
Α	1.35		1.75	0.053		0.069		
A1	0.10		0.25	0.04		0.010		
A2	1.10		1.65	0.043		0.065		
В	0.33		0.51	0.013		0.020		
С	0.19		0.25	0.007		0.010		
D	4.80		5.00	0.189		0.197		
E	3.80		4.00	0.150		0.157		
е		1.27			0.050			
Н	5.80		6.20	0.228		0.244		
h	0.25		0.50	0.010		0.020		
L	0.40		1.27	0.016		0.050		
k	8° (max.)							
ddd			0.1			0.04		

A Po Note: Drawing not in scale

Figure 28. Tape and reel SO-8 outline

Table 14. Tape and reel SO-8 mechanical data

	Dimensions						
Symbol	mm			inch			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α			330			12.992	
С	12.8		13.2	0.504		0.519	
D	20.2			0.795			
N	60			2.362			
Т			22.4			0.882	
Ao	8.1		8.5	0.319		0.335	
Во	5.5		5.9	0.216		0.232	
Ko	2.1		2.3	0.082		0.090	
Ро	3.9		4.1	0.153		0.161	
Р	7.9		8.1	0.311		0.319	

7 Revision history

Table 15. Document revision history

Date	Revision	Changes	
20-Jun-2005	2	Mistake on table 12 $t_{ZL(SHDN)}$ ms ==> μ s.	
30-Aug-2005	3	Remove (TRUE) on title, description has been updated in cover page. The V_{TH} and ΔV_{TH} values are changed in table 10.	
07-Apr-2006	4	Order codes updated.	
12-Nov-2007	5	Added Table 1.	
	013 6	Updated <i>Features on page 1</i> (added SO-8 package, replaced human body model by ±15 kV IEC 61000-4-2 air discharge and IEC 1000-4-2 by IEC 61000-4-2). Updated <i>Description on page 1</i> (renamed device to ST3485EB/EC, replaced human body model by ±15 kV IEC 61000-4-2 air discharge).	
18-Dec-2013		Removed ST3485ECN device from <i>Table 1 on page 1</i> . Updated title of <i>Table 6</i> , cross-references, replaced human body model (HBM) by ±15 kV IEC 61000-4-2 air discharge and IEC 1000-4-2 by IEC 61000-4-2. Added notes below <i>Table 9</i> .	
		Updated <i>Table 10</i> to <i>Table 12</i> (updated data, cross-references). Updated <i>Figure 5</i> to <i>Figure 16</i> (updated data, added notes below figures, highlighted some parts of <i>Figure 6</i> and <i>Figure 12</i>). Removed DIP-8 package from <i>Section 6: Package information</i> and whole document. Reformatted <i>Section 6</i> (added <i>Figure 27, Figure 28, Table 13</i> and <i>Table 14</i> , reversed order of figures and table). Minor corrections throughout document.	

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

ST PRODUCTS ARE NOT DESIGNED OR AUTHORIZED FOR USE IN: (A) SAFETY CRITICAL APPLICATIONS SUCH AS LIFE SUPPORTING, ACTIVE IMPLANTED DEVICES OR SYSTEMS WITH PRODUCT FUNCTIONAL SAFETY REQUIREMENTS; (B) AERONAUTIC APPLICATIONS; (C) AUTOMOTIVE APPLICATIONS OR ENVIRONMENTS, AND/OR (D) AEROSPACE APPLICATIONS OR ENVIRONMENTS. WHERE ST PRODUCTS ARE NOT DESIGNED FOR SUCH USE, THE PURCHASER SHALL USE PRODUCTS AT PURCHASER'S SOLE RISK, EVEN IF ST HAS BEEN INFORMED IN WRITING OF SUCH USAGE, UNLESS A PRODUCT IS EXPRESSLY DESIGNATED BY ST AS BEING INTENDED FOR "AUTOMOTIVE, AUTOMOTIVE SAFETY OR MEDICAL" INDUSTRY DOMAINS ACCORDING TO ST PRODUCT DESIGN SPECIFICATIONS. PRODUCTS FORMALLY ESCC, QML OR JAN QUALIFIED ARE DEEMED SUITABLE FOR USE IN AEROSPACE BY THE CORRESPONDING GOVERNMENTAL AGENCY.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2013 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com



DocID9102 Rev 6 21/21