

to cool to protect to connect



f.con.e 3.1

Sockets

Connectors



ISO 9001
ISO 14001
ISO 27001

Brackets

The information given in this catalogue were established and examined carefully. Nevertheless, mistakes or printing errors, and especially technical modifications and updating and improvement of our products, cannot be excluded. All trade marks are recognised even if they are not specifically identified or mentioned. No identification does not imply that a product or trademark is not registered. No part of this catalogue may be reproduced or distributed without prior written consent of Fischer Elektronik. All data contained in this catalogue, in texts, illustrations, documents and descriptions are subject to copyright and the provisions of DIN ISO 16016.

All rights reserved. © Copyright Fischer Elektronik 1969 ... 2019

Fischer Elektronik GmbH & Co. KG

P.O. Box 15 90
58465 Lüdenscheid
GERMANY

House address

Nottebohmstr. 28 • 58511 Lüdenscheid
GERMANY

Fon: +49 2351 435-0

Fax:

sales

+49 2351 45754

purchasing

+49 2351 459433

exports

+49 2351 435185






info@fischerelektronik.de
www.fischerelektronik.de



Quotations for Fischer Elektronik 1

C-print on Alu Dibond 98 x 65,5 cm

from:
Thomas Kellner
www.thomaskellner.com

A	A 1 – A 140				
B	B 1 – B 62				
C	C 1 – C 22				
D	D 1 – D 36				
E	E 1 – E 52				
F	F 1 – F 26				
G	G 1 – G 108				
H	H 1 – H 19				
I	I 1 – I 38				
K	K 1 – K 32				
L	L 1 – L 11				
M	M 1 – M 70				
N	N 1 – N 72				

Extruded profiles: extruded heatsinks, extruded heatsinks with solder pins, fin coolers, fluid coolers, high-performance heatsinks	A 1 – A 140	A
Heatsinks for processors and LED: heatsinks and fan coolers for universal PGA/BGA, DIL, PLCC, Intel Pentium Xeon, Intel Pentium IV, heatsinks for LED	B 1 – B 62	B
Board level heatsinks: finger-shaped heatsinks, heatsinks for transistors in plastic case, attachable heatsinks, small heatsinks, copper heatsinks for D PAK and others	C 1 – C 22	C
Cooling aggregates: miniature cooling aggregates, heatsink cooling aggregates, high capacity cooling aggregates, multi module cooling aggregates, hollow-fin aggregates	D 1 – D 36	D
Accessories for electronic components: thermal conductive materials, mounting parts for heatsinks, thermal conductive paste, thermally conductive adhesive, aluminium oxide and mica wafers, silicone washers, guide rails, solder stop plug, clip fastening for mounting rail	E 1 – E 52	E
Sockets: IC-sockets for DIL, PLCC, sockets for transistors, LED displays, crystal oscillators and connector-sleeves	F 1 – F 26	F
PCB connectors and accessories: male and female headers, grid spacing 2.54, 2.00 and 1.27 mm, high precision contact strips, jumpers	G 1 – G 108	G
IDC connectors: design DIL, single and double row female headers, lockable connectors, ribbon cable	H 1 – H 19	H
D-Sub connectors: male and female headers, connectors with mounting angle, connectors for ribbon cable, SMD and mixed layout, D-Sub shells, cut-out covers	I 1 – I 38	I
Brackets: brackets for PC and PCI with or without fixing tab, retainer for ISA versions	K 1 – K 32	K
Optoelectronics: LED-holders for front panel assembly, LED-holder without LED, LED-holder with mounted LED, light pipes for SMDs	L 1 – L 11	L
Cases: desk consoles, shell cases, extruded assembled cases, combination cases, tube cases, miniature aluminium cases, design cases, cooling cases, ventilation frames, feet and bushings, special front panels, sheet constructions	M 1 – M 70	M
19" Extension systems: plug-in chassis, subracks, bench cases, system cases, insert modules, part front panels, rack handles, PC-board holder, extender cards	N 1 – N 72	N

Alphanumerical product list

art. no.		page	art. no.		page	art. no.		page	art. no.		page
1706 G		F 17	BL 18 219		G 69	DB 25 WW 3		I 11	DIL 16 P		F 3
1831 Z		F 17	BL 19 141		G 69	DB 37 L		I 9	DIL 16 PEK		F 4
ASL 06 SMD	NEW	H 3	BL 19 219		G 69	DB 37 SMD TR		I 27	DIL 16 Q		F 3
ASL 08 SMD	NEW	H 3	BL 20 SMD	NEW	G 76	DB 37 T		I 8	DIL 16 SMD M		F 8
ASL 10 SMD	NEW	H 3	BL 21 650		G 65	DB 37 WW 3		I 11	DIL 16 SMD SK5 Z		F 8
ASL 12 SMD	NEW	H 3	BL 21 762		G 65	DB 50 L		I 9	DIL 18 06 E Z		F 5
ASL 14 SMD	NEW	H 3	BL 22 SHK 14 02 G	NEW	G 70	DB 50 T		I 8	DIL 18 06 H Z		F 5
ASL 16 SMD	NEW	H 3	BL 23 SHK 14 02 SMD G	NEW	G 76	DB 50 WW 3		I 11	DIL 18 E		F 4
ASL 20 SMD	NEW	H 3	BL 40 SMD 2 LED TR		G 85	DB BK 09		I 14	DIL 18 M		F 2
ASL 26 SMD	NEW	H 3	BL 40 SMD 4 LED TR		G 85	DB BK 15		I 14	DIL 20 E		F 4
ASL 34 SMD	NEW	H 3	BL 41 THR 2 LED TR		G 86	DB BK 25		I 14	DIL 20 G		F 6
ASL 40 SMD	NEW	H 3	BL 41 THR 4 LED TR		G 86	DB BK 37		I 14	DIL 20 M		F 2
ASL 50 SMD	NEW	H 3	BL 42 RDK 2 LED		G 87	DB BK 50		I 14	DIL 20 O		F 2
ASLA 06 G		H 2	BL 42 RDK 4 LED		G 87	DBM 13W3 L	NEW	I 22	DIL 20 Q		F 3
ASLA 08 G		H 2	BL KG 3		G 66	DBM 13W3 TA	NEW	I 24	DIL 20 SMD M		F 8
ASLA 10 G		H 2	BL LP 1		G 64	DBM 17W2 L	NEW	I 22	DIL 20 SMD SK5 Z		F 8
ASLA 12 G		H 2	BL LP 2		G 64	DBM 17W2 TA	NEW	I 24	DIL 22 03 M		F 2
ASLA 14 G		H 2	BL LP 3		G 64	DBM 21WA4 L	NEW	I 22	DIL 22 M		F 2
ASLA 16 G		H 2	BL LP 4		G 64	DBM 25W3 L	NEW	I 22	DIL 22 O		F 2
ASLA 20 G		H 2	BL LP 5 SMD	NEW	G 71	DBM 27W2 L	NEW	I 23	DIL 22 U		F 3
ASLA 26 G		H 2	BL LP 6 SMD	NEW	G 72	DBM 2W2C L	NEW	I 21	DIL 24 03 M		F 2
ASLA 34 G		H 2	BL LP 7 SMD	NEW	G 72	DBM 3W3 L	NEW	I 21	DIL 24 03 SMD M		F 8
ASLA 40 G		H 2	BL LP 8 LED SMD	NEW	G 84	DBM 5W5 L	NEW	I 21	DIL 24 04 M		F 2
ASLA 50 G		H 2	BL LP 9 LED	NEW	G 83	DBM 7W2 L	NEW	I 21	DIL 24 M		F 2
ASLAV 10 G	NEW	H 7	BLM 1 SMD		G 97	DBM 7W2 TA	NEW	I 24	DIL 24 U		F 3
ASLAV 20 G	NEW	H 7	BLM 2 SMD		G 97	DBM 8W8 L	NEW	I 21	DIL 28 03 M		F 2
ASLAV 26 G	NEW	H 7	BLM 3 SMD		G 97	DBM 9W4 L	NEW	I 22	DIL 28 E		F 4
ASLAV 40 G	NEW	H 7	BLM KG 1		G 94	DBM 9W4 TA	NEW	I 24	DIL 28 M		F 2
ASLG 06		H 2	BLM KG 2		G 94	DB WE 3		I 12	DIL 28 SMD M		F 8
ASLG 08		H 2	BLM LA 1		G 94	DB WE 4		I 12	DIL 32 E		F 4
ASLG 10		H 2	BLM LG 1		G 94	DB WR 3		I 12	DIL 32 M		F 2
ASLG 12		H 2	BLM LG 2		G 94	DB WR 4		I 12	DIL 36 M		F 2
ASLG 14		H 2	BLP 1		G 82	DDH 3 E		L 7	DIL 40 E		F 4
ASLG 16		H 2	BLP 2		G 82	DDH 3 M		L 7	DILS 04 PK 5		F 6
ASLG 20		H 2	BLR 1 025 Z		G 96	DDH 3 R		L 7	DILS 06 PK 3		F 6
ASLG 26		H 2	BLR 1 050 Z		G 96	DDH 3L		L 7	DILS 08 GA LO		F 7
ASLG 34		H 2	BLR 2 050 Z		G 96	DF 2 MK 9 Z		G 99	DILS 08 GB LO		F 7
ASLG 40		H 2	BLR 2 100 Z		G 96	DF 2 OK 9 Z		G 99	DILS 08 GO		F 7
ASLG 50		H 2	BLR 3 025 Z		G 96	DF OB 06		G 99	DILS 14 GA LO		F 7
ASLGV 10 G	NEW	H 7	BLR 3 050 Z		G 96	DF OB 07		G 99	DILS 14 GB LO		F 7
ASLGV 20 G	NEW	H 7	BLR 4 100 Z		G 96	DF OB 10		G 99	DILS 14 GO		F 7
ASLGV 26 G	NEW	H 7	BLR 6 SMD 100 Z		G 98	DF OB 17		G 99	DILS 14 PK 3		F 6
ASLGV 40 G	NEW	H 7	BLR 7 SMD 50 Z		G 98	DH 3 R		L 6	DILS 16 6 PK 3		F 7
ASLGY 10 G	NEW	H 4	BLV 2 10 G	NEW	G 95	DH 3 V		L 5	DILS 16 GA LO		F 7
ASLGY 20 G	NEW	H 4	BLV 2 20 G	NEW	G 95	DH 3 W		L 6	DILS 16 GB LO		F 7
ASLGY 26 G	NEW	H 4	BLV 2 26 G	NEW	G 95	DH 5 R		L 6	DILS 16 GO		F 7
ASLGY 40 G	NEW	H 4	BLV 2 30 G	NEW	G 95	DH 5 SRC		L 5	DILS 16 PK 3		F 6
ASLGY 44 G	NEW	H 4	BLV 2 40 G	NEW	G 95	DH 5 VC		L 5	DILS 16 PK 5		F 6
ASLGY 50 G	NEW	H 4	BLV 2 50 G	NEW	G 95	DH 5 W		L 6	DILS 18 GA LO		F 7
ASLV 10 SMD G	NEW	H 9	BLV 2 72 G	NEW	G 95	DH 09		I 28	DILS 18 GB LO		F 7
ASLV 20 SMD G	NEW	H 9	BLY 1		G 88	DH 09 L IP 67	NEW	I 29	DILS 18 GO		F 7
ASLV 26 SMD G	NEW	H 9	BLY 2		G 88	DH 15		I 28	DILS 18 PK 5		F 6
ASLV 40 SMD G	NEW	H 9	BLY 3		G 88	DH 15 L IP 67	NEW	I 29	DILS 24 GA LO		F 7
ASLY 10 SMD G	NEW	H 6	BLY 4		G 88	DH 25		I 28	DILS 24 GB LO		F 7
ASLY 20 SMD G	NEW	H 6	BLY 5 SMD	NEW	G 90	DH 25 L IP 67	NEW	I 29	DILS 24 GO		F 7
ASLY 26 SMD G	NEW	H 6	BLY 6 SMD	NEW	G 91	DH 37		I 28	DILS 28 6 PK 3		F 7
ASLY 40 SMD G	NEW	H 6	BLY 8 SMD		G 92	DH 50		I 28	DILS 28 GB LO		F 7
ASLY 44 SMD G	NEW	H 6	BLY 9 SMD		G 93	DH SV 09		I 29	DILS 28 GO		F 7
ASLY 50 SMD G	NEW	H 6	BLY 10 SHK 14 02 G	NEW	G 89	DH SV 15		I 29	DILS 40 6 PK 3		F 7
BADK 09	NEW	I 32	CAB 3 06 03 Z		F 15	DH SV 25		I 29	DILS 40 GA LO		F 7
BADK 15	NEW	I 32	CAB 3 08 03 Z		F 15	DH SV 37		I 29	DILS 40 GB LO		F 7
BADK 25	NEW	I 32	CAB 3 12 03 Z		F 15	DH SV 50		I 29	DILS 40 GO		F 7
BADK 37	NEW	I 32	CAB 3 14 03 Z		F 15	DIL 4 OR		F 5	DLH 21 AGEH		L 8
BADK 50	NEW	I 32	CAB 3 16 03 Z		F 15	DIL 6 E		F 4	DLH 21 AYEY		L 8
BADM 09		I 32	CAB 4 G		G 100	DIL 6 M		F 2	DS 09 L		I 9
BADM 15		I 32	CAB 5 05 G		G 100	DIL 6 P		F 3	DS 09 L IP 67	NEW	I 10
BADM 25		I 32	CAB 5 10 G		G 100	DIL 8 1 OR		F 5	DS 09 SMD TR		I 27
BADM 37		I 32	CAB 5 Z		G 100	DIL 8 2 OR		F 5	DS 09 T		I 8
BK 01 32		H 17	CAB 6 05 G		G 100	DIL 8 E		F 4	DS 09 WW 3		I 11
BL 1		G 63	CAB 6 10 G		G 100	DIL 8 G		F 6	DS 15 L		I 9
BL 2		G 63	CAB 6 Z		G 100	DIL 8 M		F 2	DS 15 L IP 67	NEW	I 10
BL 3		G 63	CAB 9 G		G 100	DIL 8 O		F 2	DS 15 SMD TR		I 27
BL 4		G 63	CAB 10 G S		G 101	DIL 8 Q		F 3	DS 15 T		I 8
BL 5		G 66	CAB 11 G S		G 101	DIL 08 SMD SK5 Z		F 8	DS 15 WW 3		I 11
BL 5 025		G 66	CAB 15 G S		G 101	DIL 10 G		F 6	DS 25 L		I 9
BL 6		G 66	CAB 16 G	NEW	G 101	DIL 10 M		F 2	DS 25 L IP 67	NEW	I 10
BL 6 025		G 66	CB 1		F 14	DIL 10 U		F 3	DS 25 SMD TR		I 27
BL 7		G 66	CB 3		F 14	DIL 14 E		F 4	DS 25 T		I 8
BL 8		G 67	CB 6		F 14	DIL 14 G		F 6	DS 25 WW 3		I 11
BL 9		G 68	DB 09 L		I 9	DIL 14 M		F 2	DS 37 L		I 9
BL 10		G 68	DB 09 L IP 67	NEW	I 10	DIL 14 N		F 2	DS 37 SMD TR		I 27
BL 11 254		G 65	DB 09 SMD TR		I 27	DIL 14 O		F 2	DS 37 T		I 8
BL 11 508		G 65	DB 09 T		I 8	DIL 14 P		F 3	DS 37 WW 3		I 11
BL 12 650		G 65	DB 09 WW 3		I 11	DIL 14 PEK		F 4	DS 50 L		I 9
BL 12 762		G 65	DB 15 L		I 9	DIL 14 U		F 3	DS 50 T		I 8
BL 13		G 68	DB 15 L IP 67	NEW	I 10	DIL 14 W 90		F 6	DS 50 WW 3		I 11
BL 14		G 68	DB 15 SMD TR		I 27	DIL 16 06 E Z		F 5	DS BK 09		I 14
BL 15 SMD 043		G 73	DB 15 T		I 8	DIL 16 06 H Z		F 5	DS BK 15		I 14
BL 15 SMD 089		G 73	DB 15 WW 3		I 11	DIL 16 E		F 4	DS BK 25		I 14
BL 16 SMD 067		G 74	DB 25 L		I 9	DIL 16 G		F 6	DS BK 37		I 14
BL 16 SMD 113		G 74	DB 25 L IP 67	NEW	I 10	DIL 16 M		F 2	DS BK 50		I 14
BL 17 SMD		G 75	DB 25 SMD TR		I 27	DIL 16 N		F 2	DSM 13W3 L	NEW	I 18
BL 18 141		G 69	DB 25 T		I 8	DIL 16 O		F 2	DSM 13W3 TA	NEW	I 20

Alphanumerical product list

art. no.		page	art. no.		page	art. no.		page	art. no.		page
DSM 17W2 L	NEW	I 18	KHPC 010		K 8	KK 20 Z		H 16	MK 03		G 2
DSM 17W2 TA	NEW	I 20	KHPC 011		K 8	KK 24 Z		H 16	MK 04		G 2
DSM 21WA4 L	NEW	I 18	KHPC 012		K 10	KK 28 Z		H 16	MK 05		G 2
DSM 25W3 L	NEW	I 18	KHPC 013		K 8	KK 40 Z		H 16	MK 06		G 59
DSM 27W2 L	NEW	I 19	KHPC 014		K 8	KK W		H 17	MK 07		G 59
DSM 2W2C L	NEW	I 17	KHPC 015		K 11	KT 0915		I 32	MK 08		G 3
DSM 3W3 L	NEW	I 17	KHPC 016		K 9	KT 2550		I 32	MK 10		G 3
DSM 5W5 L	NEW	I 17	KHPC 017		K 9	KT SV		I 30	MK 12 X 2		G 58
DSM 7W2 L	NEW	I 17	KHPC 018		K 16	LB 02 G		F 14	MK 13 X 1		G 58
DSM 7W2 TA	NEW	I 20	KHPC 019		K 14	LB 03 G		F 14	MK 13 X 2		G 58
DSM 8W8 L	NEW	I 17	KHPC 022		K 15	LB 04 G		F 14	MK 14 X 1		G 4
DSM 9W4 L	NEW	I 18	KHPC 024		K 14	LB 06 G		F 14	MK 14 X 2		G 4
DSM 9W4 TA	NEW	I 20	KHPC 026		K 17	LB SL 0508		F 15	MK 14 X 3		G 4
DS WE 3		I 12	KHPC 027		K 17	LB SL 0762		F 15	MK 15		G 4
DS WE 4		I 12	KHPC 028		K 17	LB SL 1016		F 15	MK 17		G 58
DS WR 3		I 12	KHPC 029		K 20	LB SL 1524		F 15	MK 21		G 67
DS WR 4		I 12	KHPC 031		K 20	LB SL LP 039 SMD		F 16	MK 22 SMD	NEW	G 77
D W 9 37		H 17	KHPC 032		K 20	LB SLY 06		F 15	MK 23 SMD	NEW	G 79
FLMP 06		H 11	KHPC 033		K 19	LEB 01 G		F 14	MK 24 SMD		G 78
FLMP 08		H 11	KHPC 034		K 20	LEB 02 G		F 14	MK 25 SMD		G 78
FLMP 10		H 11	KHPC 035		K 19	LEB 03 G		F 14	MK 26 SMD		G 20
FLMP 12		H 11	KHPC 036		K 20	LL 30 HRP		L 9	MK 27 SMD		G 22
FLMP 14		H 11	KHPC 038		K 13	LL 30 HRS		L 9	MK 31		G 58
FLMP 16		H 11	KHPC 040		K 13	LL 30 PRB 032		L 10	MK 51		G 4
FLMP 20		H 11	KHPC 041		K 13	LL 30 PRB 064		L 10	MK 201		G 58
FLMP 26		H 11	KHPC 042		K 16	LL 30 PRB 089		L 10	MK 202		G 2
FLMP 34		H 11	KHPC 043		K 18	LL 30 PRE 032	NEW	L 10	MK 203		G 2
FLMP 40		H 11	KHPC 051		K 20	LL 30 PRE 064	NEW	L 10	MK 204		G 2
FLMP 50		H 11	KHPC 052		K 17	LL 30 PRE 095	NEW	L 10	MK 205		G 2
FV 03		H 10	KHPC 053		K 10	LL 30 PRE 127	NEW	L 10	MK 207		G 59
FV 04		H 10	KHPC 054		K 17	LL 30 PRL 032		L 10	MK 208		G 3
FV 05		H 10	KHPC 058		K 19	LL 30 PRL 064		L 10	MK 210		G 3
FV 06		H 10	KHPC 061		K 13	LL 30 PRL 089		L 10	MK 212 X 2		G 58
FV 07		H 10	KHPC 065		K 11	LL 30 PRL 127		L 10	MK 213 X 1		G 58
FV 08		H 10	KHPC 069		K 16	LL 30 PRL 159		L 10	MK 213 X 2		G 58
FV 10		H 10	KHPC 070		K 17	LL 30 QRL 032	NEW	L 11	MK 214 X 1		G 4
FV 12		H 10	KHPC 072		K 11	LL 30 QRL 064	NEW	L 11	MK 214 X 2		G 4
FV 13		H 10	KHPC 073		K 14	LL 30 QRL 095	NEW	L 11	MK 214 X 3		G 4
FV 14		H 10	KHPC 075		K 16	LL 30 QRL 127	NEW	L 11	MK 217		G 58
FV 16		H 10	KHPC 076		K 12	LL 30 VRF5 024		L 11	MK 220 SMD		G 81
FV 17		H 10	KHPC 078		K 14	LL 30 VRF5 050		L 11	MK 221		G 67
FV 18		H 10	KHPC 085		K 22	LL 30 VRF5 075		L 11	MK 222 SMD		G 78
FV 20		H 10	KHPC 093		K 8	LL 30 WRFP 038		L 9	MK 223 SMD		G 80
FV 24		H 10	KHPC 094		K 8	LL 30 WRFP 050		L 9	MK 226 SMD		G 21
FV 25		H 10	KHPC 095		K 9	LL 30 WRFP 076		L 9	MK 228 THR		G 60
HAB 10 C	NEW	I 26	KHPC 096		K 8	LL 30 WRFP 102		L 9	MK 231		G 58
HAB 10 L	NEW	I 26	KHPC 131		K 9	LL 35 HVS		L 9	MK 251		G 4
HAB 10 TA	NEW	I 26	KHPC 138		K 10	LL 50 PRK 032	NEW	L 11	MK LP 18		G 59
HAB 20 C	NEW	I 26	KHPC 141		K 10	LL 50 PRK 064	NEW	L 11	MK LP 19		G 59
HAB 20 L	NEW	I 26	KHPC 142		K 10	LL 50 PRK 095	NEW	L 11	MK LP 40		G 5
HAB 20 TA	NEW	I 26	KHPC 143		K 11	LL 50 PRK 127	NEW	L 11	MK LP 41		G 5
HAB 40 C	NEW	I 26	KHPC 144		K 10	LL 60 WRB 254		L 10	MK LP 42		G 5
HAB 40 L	NEW	I 26	KHPC 160		K 11	MAH 31		L 2	MK LP 43		G 5
HAB 40 TA	NEW	I 26	KHPC 177		K 12	MAH 41		L 2	MK LP 218		G 59
HAS 10 C	NEW	I 25	KHPC 178		K 12	MAH 51		L 2	MK LP 219		G 59
HAS 10 L	NEW	I 25	KHPC 179		K 12	MAH 61		L 2	MK LP 240		G 5
HAS 10 TA	NEW	I 25	KHPC 185		K 13	MAH 71		L 2	MK LP 241		G 5
HAS 20 C	NEW	I 25	KHPC 187		K 13	MAH 81		L 2	MK LP 242		G 5
HAS 20 L	NEW	I 25	KHPC 188		K 14	MAH 89		L 2	PCI 0 L		K 3
HAS 20 TA	NEW	I 25	KHPC 189		K 13	MAH 99		L 2	PCI 0 O		K 3
HAS 40 C	NEW	I 25	KHPC 200		K 15	MAH 301		L 3	PCI 004		K 7
HAS 40 L	NEW	I 25	KHPC 218		K 15	MAH 302		L 3	PCI 005		K 7
HAS 40 TA	NEW	I 25	KHPC 225		K 15	MAH 303		L 3	PCI 006 O		K 7
HD B 15 L	NEW	I 13	KHPC 229		K 16	MAH 304		L 3	PCI 011		K 9
HD B 26 L	NEW	I 13	KHPC 230		K 15	MAH 305		L 3	PCI 012		K 10
HD B 44 L	NEW	I 13	KHPC 241		K 16	MAH 306		L 3	PCI 013		K 9
HD S 15 L	NEW	I 13	KHPC 242		K 16	MAH 307		L 3	PCI 014		K 14
HD S 26 L	NEW	I 13	KHPC 243		K 17	MAH 308		L 3	PCI 015		K 14
HD S 44 L	NEW	I 13	KHPC 262		K 18	MAH 309		L 3	PCI 016 L		K 17
HFD 09		I 34	KHPC 267		K 19	MAH 310		L 3	PCI 017		K 17
HFD 15		I 34	KHPC 270		K 19	MAH 401		L 2	PCI 018		K 17
HFD 25		I 34	KHPC 271		K 19	MAH 402		L 2	PCI 020		K 19
HFD 37		I 34	KHPC 277		K 19	MAH 403		L 2	PCI 021		K 21
HFK B 09		I 34	KHPC 295		K 20	MAH 404		L 2	PCI 031 O		K 12
HFK B 15		I 34	KHPC 308		K 20	MAH 405		L 2	PCI 032		K 12
HFK B 25		I 34	KHPC 325		K 21	MAH 406		L 2	PCI 033		K 13
HFK S 09		I 34	KHPC 365		K 22	MAH 407		L 2	PCI 035		K 18
HFK S 15		I 34	KHPC 391		K 22	MAH 408		L 2	PCI 039 O		K 9
HFK S 25		I 34	KHPC 398 O		K 23	MAH 409		L 2	PCI 041		K 10
ISQ 04		F 13	KHPC 404		K 23	MAH 410		L 2	PCI 045		K 14
ISQ 05		F 13	KHPC 407		K 23	MAH 501		L 3	PCI 047		K 15
ISQ 06		F 13	KHPC 439		K 24	MAH 502		L 3	PCI 051		K 23
ISQ 07		F 13	KHPC 454		K 11	MAH 503		L 3	PCI 055		K 7
ISQ 08		F 13	KHPC 455		K 15	MAH 504		L 3	PCI 065		K 12
KHPC 0 L		K 3	KHPC335L		K 22	MAH 505		L 3	PCI 071		K 15
KHPC 0 O		K 3	KK 04 Z		H 16	MAH 506		L 3	PCI 072		K 18
KHPC 002		K 8	KK 06 Z		H 16	MAH 508		L 3	PCI 076		K 18
KHPC 003		K 8	KK 08 Z		H 16	MAH 509		L 3	PCI 077		K 18
KHPC 005		K 11	KK 10 Z		H 16	MAH 510		L 3	PCI 083		K 21
KHPC 006		K 10	KK 12 Z		H 16	MIC 03		F 8	PCI 104		K 22
KHPC 007		K 8	KK 14 Z		H 16	MIC 06		F 8	PCI LP ... L		K 4
KHPC 008		K 8	KK 16 Z		H 16	MK 01		G 58	PCI LP ... O		K 4
KHPC 009		K 11	KK 18 Z		H 16	MK 02		G 2	PCI R1		K 6

Alphanumerical product list

art. no.	page	art. no.	page	art. no.	page	art. no.	page
PEK G	F 17	SIL 2	G 62	SL 11 SMD 040	NEW G 24	SL LP 1 139	G 12
PF 53	F 10	SIL 3	G 62	SL 11 SMD 052	NEW G 24	SL LP 1 164	G 12
PF 54	F 10	SK 02	F 18	SL 11 SMD 062	NEW G 24	SL LP 1 190	G 12
PF 58 2	F 10	SK 03	F 18	SL 11 SMD 078	NEW G 24	SL LP 2 082	G 12
PF 58 23	F 10	SK 04 Z	F 18	SL 11 SMD 104	NEW G 24	SL LP 2 097	G 12
PF 510	F 11	SK 05	F 18	SL 11 SMD 130	NEW G 24	SL LP 2 112	G 12
PK 1	F 17	SK 06	F 17	SL 12 SMD 031	G 25	SL LP 2 139	G 12
PK 4 Z	F 18	SK 08 G	F 18	SL 12 SMD 032	G 25	SL LP 2 164	G 12
PLCC 20	F 9	SK 11	F 18	SL 12 SMD 035	G 25	SL LP 2 190	G 12
PLCC 20 SMD	F 9	SK 13 X 2 G	F 17	SL 12 SMD 058	G 25	SL LP 3 041	G 13
PLCC 28	F 9	SK 14 X 2	F 18	SL 12 SMD 083	G 25	SL LP 3 069	G 13
PLCC 28 SMD	F 9	SK 19	F 17	SL 12 SMD 109	G 25	SL LP 4 041 ...	G 13
PLCC 32	F 9	SK 40 G	F 18	SL 13 071	G 15	SL LP 4 069	G 13
PLCC 32 SMD	F 9	SK 41	F 18	SL 13 097	G 15	SL LP 5 SMD 038	NEW G 27
PLCC 44	F 9	SK 42	F 18	SL 13 122	G 15	SL LP 5 SMD 051	NEW G 27
PLCC 44 SMD	F 9	SKB 5 Z	F 17	SL 13 147	G 15	SL LP 5 SMD 066	NEW G 27
PLCC 52	F 9	SKB 9 Z	F 17	SL 13 187	G 15	SL LP 6 SMD 038	G 28
PLCC 52 SMD	F 9	SL 1 025	G 7	SL 13 235	G 15	SL LP 6 SMD 051	G 28
PLCC 68	F 9	SL 1 053	G 7	SL 13 265	G 15	SL LP 6 SMD 066	G 28
PLCC 68 SMD	F 9	SL 1 078	G 7	SL 13 310	G 15	SL LP 7 SMD 030	G 29
PLCC 84	F 9	SL 1 104	G 7	SL 13 365	G 15	SL LP 7 SMD 040	G 29
PLCC 84 SMD	F 9	SL 1 128	G 7	SL 14 071	G 15	SL LP 7 SMD 055	G 29
PO A	G 61	SL 1 154	G 7	SL 14 097	G 15	SLM N 1 063	G 48
PQ 18	F 13	SL 1 179	G 7	SL 14 122	G 15	SLM N 1 092	G 48
PQ 18 W	F 13	SL 1 230	G 7	SL 14 147	G 15	SLM N 1 117	G 48
PSB 03 G	F 14	SL 2 025	G 8	SL 14 187	G 15	SLM N 11 063	G 48
PV 06	H 12	SL 2 053	G 8	SL 14 235	G 15	SLM N 11 117	G 48
PV 10	H 12	SL 2 078	G 8	SL 14 265	G 15	SLP 1 16 117	G 32
PV 14	H 12	SL 2 104	G 8	SL 14 310	G 15	SLP 1 16 129	G 32
PV 16	H 12	SL 2 128	G 8	SL 14 365	G 15	SLP 1 16 144	G 32
PV 20	H 12	SL 2 154	G 8	SL 15 SMD 107	G 30	SLP 1 16 195 Z	G 32
PV 26	H 12	SL 2 179	G 8	SL 15 SMD 182	G 30	SLP 2 16 117	G 32
PV 34	H 12	SL 2 230	G 8	SL 15 SMD 207	G 30	SLP 2 16 129	G 32
PV 40	H 12	SL 3 025	G 10	SL 16 SMD 107	G 30	SLP 2 16 144	G 32
PV 50	H 12	SL 3 053	G 10	SL 16 SMD 157	G 30	SLP 2 16 195 Z	G 32
PVV 10 G	NEW H 14	SL 3 080	G 10	SL 16 SMD 182	G 30	SLR 1 025	G 55
PVV 20 G	NEW H 14	SL 3 101	G 10	SL 16 SMD 207	G 30	SLR 1 050	G 55
PVV 26 G	NEW H 14	SL 3 131	G 10	SL 16 SMD 247	G 30	SLR 2 050	G 55
PVV 40 G	NEW H 14	SL 3 152	G 10	SL 17 SMD 058	G 26	SLR 3 025	G 55
PV W	H 17	SL 3 182	G 10	SL 17 SMD 083	G 26	SLR 3 050	G 55
PVY 10 S	NEW H 13	SL 3 207	G 10	SL 17 SMD 109	G 26	SLR 4 050	G 55
PVY 20 S	NEW H 13	SL 4 025	G 10	SL 18 042	G 11	SLR 4 100	G 55
PVY 26 S	NEW H 13	SL 4 101	G 10	SL 18 082	G 11	SLR 5 SMD 50 G	G 56
PVY 40 S	NEW H 13	SL 4 152	G 10	SL 18 108	G 11	SLU 10 165	G 17
PVY 44 S	NEW H 13	SL 5 071	G 14	SL 18 132	G 11	SLU 10 191	G 17
PVY 50 S	NEW H 13	SL 5 097	G 14	SL 19 082	G 11	SLU 10 241	G 17
PVY W	H 17	SL 5 121	G 14	SL 19 108	G 11	SLU 10 266	G 17
QS 25 GS	F 13	SL 5 147	G 14	SL 19 132	G 11	SLU 16 165	G 17
RAH 503	NEW L 4	SL 5 156 G	G 14	SL 20 THR 097	G 9	SLU 16 191	G 17
RAH 504	NEW L 4	SL 5 156 Z	G 14	SL 20 THR 112	G 9	SLU 16 241	G 17
RAH 505	NEW L 4	SL 5 172	G 14	SL 20 THR 124	G 9	SLU 16 266	G 17
RAH 506	NEW L 4	SL 5 197	G 14	SL 20 THR 139	G 9	SLU 20 165	G 17
RAH 507	NEW L 4	SL 5 223	G 14	SL 20 THR 164	G 9	SLU 20 191	G 17
RAH 508	NEW L 4	SL 5 237	G 14	SL 21 THR 097	G 9	SLU 20 241	G 17
RAH 509	NEW L 4	SL 5 285	G 14	SL 21 THR 112	G 9	SLU 20 266	G 17
RAH 510	NEW L 4	SL 5 315	G 14	SL 21 THR 124	G 9	SLU 26 165	G 17
RJ 45 G	NEW I 7	SL 5 360	G 14	SL 21 THR 139	G 9	SLU 26 191	G 17
RJ 45 LED	NEW I 7	SL 5 415	G 14	SL 21 THR 164	G 9	SLU 26 241	G 17
RJ 45 U	NEW I 7	SL 5 525	G 14	SL 22 097	G 8	SLU 26 266	G 17
RS HH	I 29	SL 6 071	G 14	SL 22 112	G 8	SLU 40 165	G 17
RS SH 3	I 30	SL 6 097	G 14	SL 22 124	G 8	SLU 40 191	G 17
RS SH 4	I 30	SL 6 121	G 14	SL 22 139	G 8	SLU 40 241	G 17
RS SH D	I 30	SL 6 147	G 14	SL 22 164	G 8	SLU 40 266	G 17
SB 1	F 19	SL 6 156 G	G 14	SL 22 190	G 8	SLU 50 165	G 17
SB 2	F 19	SL 6 156 Z	G 14	SL 22 214	G 8	SLU 50 191	G 17
SB 3	F 19	SL 6 172	G 14	SL 22 240	G 8	SLU 50 241	G 17
SB 4	F 19	SL 6 197	G 14	SL 22 265	G 8	SLU 50 266	G 17
SB 5	F 19	SL 6 223	G 14	SL 22 316	G 8	SLUP 31 10	G 33
SB 6	F 19	SL 6 237	G 14	SL 23 LED SMD 031	NEW G 36	SLUP 31 16	G 33
SB 9	F 20	SL 6 285	G 14	SL 23 LED SMD 058	NEW G 36	SLUP 31 20	G 33
SB 12	F 20	SL 6 315	G 14	SL 24 LED 097	NEW G 34	SLV N 1 055	G 48
SB 13	F 20	SL 6 360	G 14	SL 24 LED 112	NEW G 34	SLV N 1 080	G 48
SB 15	F 20	SL 6 415	G 14	SL 24 LED 124	NEW G 34	SLV N 1 105	G 48
SB 16	F 20	SL 6 525	G 14	SL 25 LED THR 097	NEW G 35	SLV N 1 130	G 48
SBAU 1 04	H 15	SL 7	G 6	SL 25 LED THR 112	NEW G 35	SLV N 11 055	G 48
SBAU 1 06	H 15	SL 8	G 6	SL 25 LED THR 124	NEW G 35	SLV N 11 080	G 48
SBAU 1 08	H 15	SL 9	G 6	SL 26 SHK 14 02 G	NEW G 19	SLV N 11 105	G 48
SBAU 1 10	H 15	SL 10 SMD 040	NEW G 23	SL 27 SHK 14 02 SMD G	NEW G 31	SLV W 1 055	G 49
SBAU 1 12	H 15	SL 10 SMD 052	NEW G 23	SL 40 SMD 2 LED TR	G 37	SLV W 1 080	G 49
SBAU 1 14	H 15	SL 10 SMD 062	NEW G 23	SL 40 SMD 4 LED TR	G 37	SLV W 1 105	G 49
SBAU 1 16	H 15	SL 10 SMD 078	NEW G 23	SL 41 THR 2 LED TR	G 38	SLV W 1 130	G 49
SBAU 1 17	H 15	SL 10 SMD 104	NEW G 23	SL 41 THR 4 LED TR	G 38	SLV W 1 KA 030	G 51
SBAU 1 18	H 15	SL 10 SMD 130	NEW G 23	SLK 3 025	G 10	SLV W 1 KA 055	G 51
SBAU 1 20	H 15	SL 11 097	G 7	SLK 4 025	G 10	SLV W 1 KA 080	G 51
SBAU 06 Z	H 15	SL 11 112	G 7	SL KA 3 072	G 18	SLV W 1 KA 105	G 51
SBAU 10 Z	H 15	SL 11 124	G 7	SL KA 3 085	G 18	SLV W 1 SMD 048	G 53
SBAU 14 Z	H 15	SL 11 139	G 7	SL KA 3 108	G 18	SLV W 1 SMD 073	G 53
SBAU 16 Z	H 15	SL 11 164	G 7	SL KG 3 113	G 18	SLV W 2 055	G 49
SBAU 20 Z	H 15	SL 11 190	G 7	SL KG 3 126	G 18	SLV W 2 080	G 49
SBAU 26 Z	H 15	SL 11 214	G 7	SL KG 3 147	G 18	SLV W 2 105	G 49
SBAU 34 Z	H 15	SL 11 240	G 7	SL LP 1 082	G 12	SLV W 2 130	G 49
SB W	H 17	SL 11 265	G 7	SL LP 1 097	G 12	SLV W 2 KA 030 10	G 51
SIL 1	G 62	SL 11 316	G 7	SL LP 1 112	G 12	SLV W 2 KA 030 14	G 51

Alphanumerical product list

art. no.	page	art. no.	page
SLV W 2 KA 030 16	G 51	SLY 10 SMD 040	G 46
SLV W 2 KA 030 20	G 51	SLY 11 SMD 051	NEW G 47
SLV W 2 KA 030 26	G 51	SLY 11 SMD 092	NEW G 47
SLV W 2 KA 030 30	G 51	SLY 11 SMD 133	NEW G 47
SLV W 2 KA 030 34	G 51	SLY 12 SMD 051	NEW G 47
SLV W 2 KA 030 40	G 51	SLY 12 SMD 092	NEW G 47
SLV W 2 KA 030 50	G 51	SLY 12 SMD 133	NEW G 47
SLV W 2 KA 030 72	G 51	SLY 13 SHK 14 02 G	NEW G 42
SLV W 2 KA 054 10	G 51	SLY 14 SHK 14 02 G	NEW G 42
SLV W 2 KA 054 14	G 51	SSK B 09	I 35
SLV W 2 KA 054 16	G 51	SSK B 15	I 35
SLV W 2 KA 054 20	G 51	SSK B 25	I 35
SLV W 2 KA 054 26	G 51	SSK B 37	I 35
SLV W 2 KA 054 30	G 51	SSK S 09	I 35
SLV W 2 KA 054 34	G 51	SSK S 15	I 35
SLV W 2 KA 054 40	G 51	SSK S 25	I 35
SLV W 2 KA 054 50	G 51	SSK S 37	I 35
SLV W 2 KA 054 72	G 51	TF 3 2	F 11
SLV W 2 SMD 048	G 53	TF 53	F 12
SLV W 2 SMD 073	G 53	TF 54	F 12
SLV W 3 SMD 048	G 54	TF 56	F 12
SLV W 3 SMD 073	G 54	TF 58	F 12
SLV W 4 055	NEW G 50	TF 183	F 12
SLV W 4 080	NEW G 50	TF 184	F 12
SLV W 4 105	NEW G 50	TF 510	F 12
SLV W 4 130	NEW G 50	TF G	F 17
SLV W 4 KA 036 10	NEW G 52	USB 2 A 90	NEW I 2
SLV W 4 KA 036 14	NEW G 52	USB 2 A 90 V	NEW I 2
SLV W 4 KA 036 16	NEW G 52	USB 2 A 180	NEW I 2
SLV W 4 KA 036 20	NEW G 52	USB 2 A SMD	NEW I 4
SLV W 4 KA 036 26	NEW G 52	USB 2 B 90	NEW I 3
SLV W 4 KA 036 30	NEW G 52	USB 2 B 180	NEW I 3
SLV W 4 KA 036 34	NEW G 52	USB 2 B SMD	NEW I 4
SLV W 4 KA 036 40	NEW G 52	USB 3 A 90	NEW I 6
SLV W 4 KA 036 50	NEW G 52	USB 3 A 90 V	NEW I 6
SLV W 4 KA 036 72	NEW G 52	USB 31 C	NEW I 6
SLV W 4 KA 060 10	NEW G 52	USB MC 2 B SMD	NEW I 5
SLV W 4 KA 060 14	NEW G 52	USB MN 2 B	NEW I 3
SLV W 4 KA 060 16	NEW G 52	USB MN 2 B SMD	NEW I 4
SLV W 4 KA 060 20	NEW G 52	V	I 33
SLV W 4 KA 060 26	NEW G 52	V 2	I 33
SLV W 4 KA 060 30	NEW G 52	VBK 1	H 17
SLV W 4 KA 060 34	NEW G 52	VFL 06	H 11
SLV W 4 KA 060 40	NEW G 52	VFL 08	H 11
SLV W 4 KA 060 50	NEW G 52	VFL 10	H 11
SLV W 4 KA 060 72	NEW G 52	VFL 12	H 11
SLV W 4 SMD 048	NEW G 53	VFL 14	H 11
SLV W 4 SMD 073	NEW G 53	VFL 16	H 11
SLV W 11 055	G 49	VFL 20	H 11
SLV W 11 080	G 49	VFL 26	H 11
SLV W 11 105	G 49	VFL 34	H 11
SLV W 22 055	G 49	VFL 40	H 11
SLV W 22 080	G 49	VFL 50	H 11
SLV W 22 105	G 49	VG 2	I 33
SLY 1 081	G 39	VSLGV 10 G	NEW H 8
SLY 1 085	G 39	VSLGV 20 G	NEW H 8
SLY 1 098	G 39	VSLGV 26 G	NEW H 8
SLY 1 104	G 39	VSLGV 40 G	NEW H 8
SLY 1 139	G 39	VSLGY 10 G	NEW H 5
SLY 2 081	G 39	VSLGY 20 G	NEW H 5
SLY 2 085	G 39	VSLGY 26 G	NEW H 5
SLY 2 098	G 39	VSLGY 40 G	NEW H 5
SLY 2 104	G 39	VSLGY 44 G	NEW H 5
SLY 2 139	G 39	VSLGY 50 G	NEW H 5
SLY 3 035	G 39	VSLV 10 SMD G	NEW H 9
SLY 3 041	G 39	VSLV 20 SMD G	NEW H 9
SLY 3 082 ... G	G 39	VSLV 26 SMD G	NEW H 9
SLY 3 082 ... Z	G 39	VSLV 40 SMD G	NEW H 9
SLY 4 035	G 39	WWPS 1 G	F 17
SLY 4 082 ... G	G 39	ZEPV 06	H 12
SLY 4 082 ... Z	G 39	ZEPV 10	H 12
SLY 4 041... G	G 39	ZEPV 14	H 12
SLY 4 041... Z	G 39	ZEPV 16	H 12
SLY 5 040	G 40	ZEPV 20	H 12
SLY 5 075	G 40	ZEPV 26	H 12
SLY 5 081 ... G	G 40	ZEPV 34	H 12
SLY 5 081 ... Z	G 40	ZEPV 40	H 12
SLY 5 122 ... G	G 40	ZEPV 50	H 12
SLY 5 122 ... Z	G 40		
SLY 6 040	G 40		
SLY 6 075	G 40		
SLY 6 081 ... G	G 40		
SLY 6 081 ... Z	G 40		
SLY 6 122 ... G	G 40		
SLY 6 122 ... Z	G 40		
SLY 7 SMD 036	G 43		
SLY 7 SMD 045	G 43		
SLY 7 SMD 062	G 43		
SLY 8 SMD 036	G 44		
SLY 8 SMD 045	G 44		
SLY 8 SMD 062	G 44		
SLY 9 SMD 040	G 45		
SLY 9 SMD 055	G 45		

Brackets for PC	K 3-24
Connector-sleeves	F 19-20
Direct female connectors	G 99
D-Sub accessories	I 32-35
D-Sub connector for flat ribbon cable	I 14-16
D-Sub connectors High Density	I 13
D-Sub hoods	I 28-31
D-Sub in SMD-mounting	I 27
D-Sub mixed layout connectors	I 17-24
D-Sub standard connectors	I 8-12
Female connector	H 10-14
Female headers	G 58-98
High-precision contacts, loose	F 17-18
High-precision sockets and plugs for DIL-IC	F 2-8
Jumper links / Separable jumpers	F 14-16
Jumpers	G 100-101
LED-holders	L 5-8
Light pipes for SMDs	L 9-11
Male headers	G 2-57
Pin contacts, loose	I 25
Printed circuit connector	H 15-17
RJ 45 connectors	I 7
Shroud-male header	H 2-9
Socket contact, loose	I 26
Sockets for crystal oscillators	F 13
Sockets for IC-PLCC	F 9
Sockets for TO ... cases	F 10-12
Spacers for LED	L 2-4
USB connectors	I 2-6




foyer of the company




motivated employees



committed field service



innovative product development




certified quality management



own tool-making department



foresighted storekeeping



efficient special machines



up-to-date injection technology



modern surface refinement

Quality-Management System ISO 9001

We are certified to ISO 9001.

This process-directed quality management system implies a constant focus on satisfying the demands of customers, and this is the major objective of our company.

The implementation and further development of our quality management system demonstrably ensures

- guaranteed customer satisfaction and thus the success of our company,
- compliance with customers' requirements at all times through defined processes,
- early detection and prevention of errors, and
- checking of both process effectiveness and efficiency on a regular basis together with steady improvement.

It is through constant vigilance and the provision of evidence that we deliver flawless products, which fully comply with quality requirements, that we maintain our quality certification.

In order to secure lasting company success and to meet our customers' expectations now and in the future, we define measurable objectives within the framework of our quality system, which are regularly checked and developed.

We are committed to constant measurement and improvement of our performance.

Our quality management system applies to all processes carried out by our company.

Certificate

Standard **ISO 9001:2015**

Certificate Registr. No. **09 100 4274**

Certificate Holder:

fischer elektronik 

Fischer Elektronik GmbH & Co. KG
Nottebohmstr. 28
58511 Lüdenscheid
Germany

Scope:

Design/construction, manufacture, assembly and technical advice for heatsinks, sockets, connectors, mounting parts, cases, 19" assembly systems, computer accessories

Proof has been furnished by means of an audit that the requirements of ISO 9001:2015 are met.

Validity:

The certificate is valid from 2018-11-01 until 2021-10-31.
First certification 1994

2018-10-17


TÜV Rheinland Cert GmbH
Am Grauen Stein · 51105 Köln

Certificate

Standard **ISO 14001:2015**

Certificate Registr. No. **01 104 8209**

Certificate Holder:

fischer elektronik 

Fischer Elektronik GmbH & Co. KG
Nottebohmstr. 28
58511 Lüdenscheid
Germany

Scope:

Design/construction, manufacture, assembly and technical advice for heatsinks, sockets, connectors, mounting parts, cases, 19" assembly systems, computer accessories

Proof has been furnished by means of an audit that the requirements of ISO 14001:2015 are met.

Validity:

The certificate is valid from 2018-10-09 until 2021-10-08.
First certification 1998

2018-10-17


TÜV Rheinland Cert GmbH
Am Grauen Stein · 51105 Köln

www.tuv.com



Environmental Management System ISO 14001

We consider protection of the environment and saving of natural resources entrepreneurial tasks of high priority.

Aware of this, our company was the first German heat-sink manufacturer to implement the environmental management system in accordance with ISO 14001 in 1998.

Our entrepreneurial responsibility comprises preventing accidents, safeguarding against occupational diseases, designing workplaces to suit human requirements, developing products which are safe to use, saving resources and avoiding environmental impact to the maximum extent possible.

We already consider environmental compatibility in the product and process development stage. The environmental impact of our activities is documented, assessed and in a continuous improvement process reduced to a minimum.

Implementation and consistent working on and with the environmental management system is a vital process and a constant challenge but finally it will always lead to better results.

www.tuv.com



Information management norm DIN EN ISO/IEC 27001

Information security is becoming more important. For the success of our business information are essential values. Administering and protecting those has our top priority.

The information security management system to ISO/IEC 27001 considers three kinds of information: availability, confidentiality and integrity.

This information security management system is the basis for continuous monitoring and optimisation processes. It also ensures the scrupulous handling with information. A protection against attacks on the corporate network and theft is ensured.

Within the information security management system the risk evaluation such as human misconduct takes place by means of error-possibility-influence-analysis.



Europäische Gemeinschaft

AEO-Zertifikat

1. Inhaber des AEO-Zertifikats

Fischer Elektronik GmbH & Co KG
EORI-Nummer: DE 2499770
Nr. der aml. Eintragung: HRA 2836
UST-IDNr(n): DE 125797501

DE AEOC 101367
(Nummer des Zertifikats)

2. Erteilende Behörde
Hauptzollamt Dortmund
Kronenburgallee 7
DE-44139 Dortmund



Der in Feld 1 genannte Inhaber ist

Zugelassener Wirtschaftsbeteiligter

"AEOC (zollrechtliche Vereinfachungen)"

3. Tag, ab dem das Zertifikat wirksam ist:

16.03.2010

Certificate

Standard **ISO/IEC 27001:2013**

Certificate Registr. No. **01 153 101878**

Certificate Holder: **fischer elektronik**

Fischer Elektronik GmbH & Co. KG
Nottebohmstr. 28
58511 Lüdenscheid
Germany

Scope: Design/construction, manufacture, assembly and sales for
heatsinks, sockets, connectors, mounting parts, cases,
19" assembly systems, PCB accessory

SoA Version 2.0 from 04.09.2017

Proof has been furnished by means of an audit that the
requirements of ISO/IEC 27001:2013 are met.

Validity: The certificate is valid from 2017-10-01 until 2020-09-30.
First certification 2011

2017-10-24

TÜV Rheinland Cert GmbH
Am Grauen Stein · 51105 Köln

www.tuv.com



The authorised economic operator AEO-certificate

Since 1st January 2008 companies based in the European Union and involved in customs activities have been able to apply for the status of Authorised Economic Operator (AEO). The status entitles a benefit of safety-relevant custom controls and/or simplification according to custom regulations.

The goal is here to ensure an uninterrupted global supply chain from the producer to the end user. The status of an authorised economic operator is valid in all Member States and is not limited in time.

Our company has the status AEO-C (customs simplification).

The legal requirements of an authorised economic operator are essentially the result of:

Article 5a community custom code (ZK)

Article 14a - 14x community custom code implementing provision (ZK-DVO)



Electronica, Fair Munich

D



Embedded World, Exhibition Center Nuremberg

D



Light + Building, Fair Frankfurt

D



Enova, Porte de Versailles Paris

FR




PCIM, Exhibition Center Nuremberg

D

 Berlin D 05. 11. - 07. 11. 2019 www.light-building.de Berlin ExpoCenterCity hall 2.2, stand 325	 Nuremberg D 26. 11. - 28. 11. 2019 www.embedded-world.de Exhibition Center Nuremberg hall 3C, stand 744	 Nuremberg D 25. 02. - 27. 02. 2020 www.embedded-world.de Exhibition Center Nuremberg hall 4A, stand 516
 Frankfurt D 08. 03. - 13. 03. 2020 www.light-building.de Exhibition Frankfurt hall 8.0, stand H24	 Munich D 10. 11. - 13.11. 2020 www.electronica.de Exhibition Munich	 Nuremberg D 02. 03. - 04. 03. 2021 www.embedded-world.de Exhibition Center Nuremberg

Explanations – references – printings



... index area:
shows topics/categories
"current"



... index area:
shows topics/categories
"following"

... page number

Male headers 2.00 THT	→ G 50 - 52
Male headers 2.54 THT	→ G 8 - 18
Technical data	→ G 72 - 76
Flat cable	→ H 11


G = gold-plated
Z = tin-plated
S = selective gold-plated



... footnotes, give references to pages with combinable or similar products

... option for surface finishing

... plastic of the insulator is suitable for reflow-soldering up to 260 °C




... components are suitable for soldering technique (THT)




... components are suitable for SMD technique



... components are suitable for THR-SMD technique



... components are suitable for press-fit mounting



... components are suitable for the corresponding grid

Imprinting of cardholders - Your and our time is expensive

An order for imprinting must state the font, the font size and the exact position of the imprint with dimensions, taking in account of countersunk holes etc.. When placing the first order, the company logo must be supplied as a vector file. If these conditions are not complied with, the order for imprinting may have to be rejected, or additional costs will have to be charged.

Compliance with the following criteria ensures smooth handling:

Adobe Illustrator (.ai; .eps)	without half-tone images, fonts transformed into paths or supplied
Adobe Acrobat (.pdf)	all fonts enclosed; half-tone images colour-separated (full-tone or scale colours) and
InDesign (.indd)	with correct resolution (300 dpi colour, black / white 600 dpi), no RGB

All this takes additional time and consequently incurs extra costs.

The usability must be checked by our printing shop:

In most cases screen formats (.jpg, .gif, .png) and paper copies, stickers and similar are not suitable for preparing printer's copies!

Copies that definitely cannot be used:

Imperfect copies such as fax copies / Microsoft Office files (.doc, .xls, .ppt) can only be used for information or for transmitting texts.

Please always add dimensional drawings (.dxf) to the parts to be imprinted!

Please note as a general rule: Retouching work extending beyond the standard time will be invoiced additionally at cost price.

No part of this catalogue may be reproduced or distributed without prior written consent of Fischer Elektronik.

All data contained in this catalogue, in texts, illustrations, documents and descriptions are subject to copyright and the provisions of DIN ISO 16016. All rights reserved.

© Copyright Fischer Elektronik 1969 ... 2019

General points

Product specified characteristics for the particular article can be found in the category "technical data"! Additional customer specified advice and solution proposals will be supported from the R&D department of company Fischer Elektronik GmbH & Co. KG.

Surface – electroplating processes

In general all contacts are coated with a nickel barrier layer (1.3-3 µm) before they get tinned or gold-plated. This will also apply for selective gold-plated contacts.

For the selective coated contacts the complete contact will be nickel-plated including the carrier strip first. After this the contact side will be gold-plated and the solder side tinned, usually in the "dipping method" or "brush method". Depending on the overall contact length the middle area is exclusively nickel-plated.

The layer thickness of the gold-plating is at least 0.2 µm Au, the layer thickness of the tinning is 4-6 µm! Other layer thicknesses are possible upon request.

The tinning is done with pure tin. The solderability is guaranteed for at least 1 year after shipment. At appropriate storage in closed packing this period can be increased significantly.

Dimensional tolerance

Generally the DIN ISO 2768m is applied to all products! Moreover following additions have to be noticed:

- the length tolerance of contact pins is +/-0.2 mm
- the space allowance is +/-0.03 mm, the overall space allowance over 36 pins +/-0.2 mm
- the shape tolerance of the insulating body is defined by +/-0.15 mm
- the separation of number of pins by means of cutting: +0.6 mm/-0.3 mm
- the separation of number of pins by means of sawing: +0.1 mm/-0.4 mm (no standard)

Quality grading in conformity with DIN 41652

Depending on the layer thickness of the gold-plating the contacts can be classified in quality classes.

A distinction is made in three quality classes:

Quality class 1: at least 500 cycles of operation, layer thickness accordingly at least 1.2 µm Au

Quality class 2: at least 200 cycles of operation, layer thickness accordingly at least 0.75 µm Au

Quality class 3: at least 50 cycles of operation, layer thickness accordingly at least 0.2 µm Au

In case that tinned contacts are used „tin on tin“ we can guarantee max. 10 cycles of operation.


Precision socket contacts

These contacts are two-piece parts and consist on a sleeve (turned part) and a spring element (stamped part). The spring element (clip) is always gold-plated (depending on the article at least 0.2 µm Au or at least 0.75 µm Au). The sleeve is usually tinned, for some versions also optionally gold-plated (at least 0.2 µm Au).

Contact carrier material made of high-temperature resistant plastic


The plastics used for the male and female headers are mainly high-temperature resistant which means that they are suitable for the use in the reflow soldering technique.

This applies primarily for SMD components as well as for plug connectors which are constructed for wave soldering. In the catalogue those products are marked with a 260 °C logo in the header of the particular page.




Precision sockets and plugs for ICs with high packing density

- PLCC-socket for soldering technology (THT)
- PLCC-socket for SMD technology - low profile
- type of packaging: bar magazine




Precision sockets and plugs for DIL-ICs

- precision sockets and plugs in soldering (THT) and SMD technology
- DIL-IC sockets with extractor
- open and closed design



Customer specified DIL-IC sockets

- sockets for LED displays
- Dual-in-line plug in adapter
- IC-sockets partially loaded with oscillators and relays




Mounting sockets for discrete components, jumper links and connectors


- sockets for TO 5 cases
- plug-in sockets for crystal oscillators
- jumper links with and without insulators
- precision pins and bushings, bulk
- connectors, with and without insulator

High-precision sockets and plugs for DIL-IC

– other number of contacts upon request!




art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
		A	B	C	D			A	B	C	D
DIL 6 M ...	6	7.62	10.1	3.8	7.6	DIL 22 M ...	22	10.16	12.7	6.6	27.9
DIL 8 M ...	8				10.1	DIL 24 03 M ...	24	7.62	10.1	4.0	30.6
DIL 10 M ...	10			4.7	12.7	DIL 24 04 M G		10.16	12.7	7.1	
DIL 14 M ...	14			4.9	17.7	DIL 24 M ...		15.24	17.7	11.6	
DIL 16 M ...	16			3.5	20.4	DIL 28 03 M ...	28	7.62	10.1	4.0	35.7
DIL 18 M ...	18			4.1	23.0	DIL 28 M ...		15.24	17.7	11.3	
DIL 20 M ...	20			3.4	25.5	DIL 32 M ...	32			11.2	40.6
DIL 22 03 M Z	22			4.8	27.9	DIL 36 M G	36			10.6	45.6



art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
		A	B	C	D			A	B	C	D
DIL 14 N ...	14	7.62	10.1	4.9	17.7	DIL 16 N ...	16	7.62	10.1	3.5	20.4

please indicate: ... surface of contact
G = gold-plated
Z = tin-plated

contact spring: gold-plated










art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
		A	B	C	D			A	B	C	D
DIL 8 O ...	8	7.62	10.1	3.8	10.1	DIL 20 O G	20	7.62	10.1	3.4	25.5
DIL 14 O ...	14			4.9	17.7	DIL 22 O ...	22	10.16	12.7	6.6	27.9
DIL 16 O ...	16			3.5	20.4						




please indicate: ... surface of contact
G = gold-plated
Z = tin-plated

High-precision sockets and plugs for DIL-IC



– other number of contacts on request!

											
art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
DIL 6 P Z	6	7.62	10.1	3.8	7.6	DIL 16 P Z	16	7.62	10.1	3.5	20.4
DIL 14 P Z	14			4.9	17.7						
											
art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
DIL 8 Q G	8	7.62	10.1	3.8	10.1	DIL 20 Q Z	20	7.62	10.1	3.4	25.5
DIL 16 Q Z	16			3.5	20.4						
											
art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
DIL 10 U Z	10	7.62	10.1	4.7	12.7	DIL 22 U ...	22	10.16	12.7	6.6	27.9
DIL 14 U G	14			4.9	17.7	DIL 24 U ...	24	15.24	17.7	11.6	30.6
please indicate: ... surface of contact G = gold-plated Z = tin-plated											

Socket layout for various numbers of contacts for DIL-IC, open frame

6-16 pol.	18-32 pol.	36 pol.
		




High-precision sockets and plugs for DIL-IC

									
art. no.	no. of contacts	dim. [mm]			art. no.	no. of contacts	dim. [mm]		
DIL 6 E ...	6	7.62	10.3	7.6	DIL 20 E ...	20	7.62	10.3	25.5
DIL 8 E ...	8			10.1	DIL 28 E ...	28	15.24	17.7	35.5
DIL 14 E ...	14			17.7	DIL 32 E ...	32			40.6
DIL 16 E ...	16			20.4	DIL 40 E ...	40			50.8
DIL 18 E ...	18			23.0					
please indicate: ... surface of contact G = gold-plated Z = tin-plated									
contact spring:				gold-plated					

Socket layout for various numbers of contacts for DIL-IC, closed frame

6 pol.	8 pol.	14-22 pol.
28 pol.	32-40 pol.	

DIL-IC-sockets with extractor





															
art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]							
		A	B	C	D			A	B	C	D				
DIL 14 PEK	14	7.62	10.1	12	17.0	DIL 16 PEK	16	7.62	10.1	12	20.3				
contact spring:			gold-plated												
contact sleeve:			gold-plated												

High-precision sockets and plugs for DIL-IC

IC-sockets partially equipped, e.g. for oscillators and relays




art. no.	no. of contacts			
DIL 4 OR ...	4			
DIL 8 1 OR Z	8			
DIL 8 2 OR ...				
please indicate:	... surface of contact G = gold-plated Z = tin-plated			
contact spring:	gold-plated			



LED display sockets of 0.6" pitch

										
art. no.	no. of contacts	dim. [mm] A			art. no.	no. of contacts	dim. [mm] A			
DIL 16 06 E Z	16	20.3			DIL 18 06 E Z	18	22.8			
										
art. no.	no. of contacts	dim. [mm] A			art. no.	no. of contacts	dim. [mm] A			
DIL 16 06 H Z	16	20.3			DIL 18 06 H Z	18	22.8			
contact spring:		gold-plated								
contact sleeve:		tin-plated								





High-precision sockets and plugs for DIL-IC

LED display sockets in vertical construction



				
art. no.	no. of contacts	dim. [mm]		
DIL 14 W 90	14	A 27.7	B 22.7	
contact spring:		gold-plated		
contact sleeve:		tin-plated		

										
art. no.	no. of contacts	dim. [mm] A			art. no.	no. of contacts	dim. [mm] A			
DIL 8 G Z	8	10.1			DIL 16 G ...	16	20.3			
DIL 10 G ...	10	12.7			DIL 20 G ...	20	25.4			
DIL 14 G ...	14	17.7								
please indicate: ... surface of contact G = gold-plated Z = tin-plated										
contact spring:					gold-plated					

DIL adaptor plugs



		PK 3		SK 02 (≅ PK 5)		PK 3		SK 02 (≅ PK 5)	
									
art. no.		no. of contacts	dim. [mm]		art. no.		no. of contacts	dim. [mm]	
			A	B				A	B
DILS 04 PK 5		4	5.0	2.54	DILS 16 PK 3		16	20.3	17.78
DILS 06 PK 3		6	7.6	5.08	DILS 16 PK 5				
DILS 14 PK 3		14	17.7	15.24	DILS 18 PK 5		18	23.0	20.32
surface of contact:			gold-plated						

High-precision sockets and plugs for DIL-IC

						
	art. no.	no. of contacts	dim. [mm] A B	art. no.	no. of contacts	dim. [mm] A B
	DILS 28 6 PK 3	28	35.5 33.02	DILS 16 6 PK 3	16	20.3 17.78
	DILS 40 6 PK 3	40	50.8 48.26			
surface of contact:		gold-plated				



DIL platforms

– suitable for **DIL-cases** DILS ... GA LO

						
	art. no.	no. of contacts	dim. [mm] A B C	art. no.	no. of contacts	dim. [mm] A B C
	DILS 08 GO	8	12.4 12.5 7.62	DILS 24 GO	24	32.8 20.1 15.24
	DILS 14 GO	14	20.0	DILS 28 GO	28	37.8
	DILS 16 GO	16	22.6	DILS 40 GO	40	53.1
	DILS 18 GO	18	25.2			
surface of contact:		gold-plated				

DIL cases - grid spacing 2.54 mm



– suitable for **DIL** plugs DILS ... GO

							
art. no.	dim. [mm]			art. no.	dim. [mm]		
	B	H	L		B	H	L
DILS 08 GA LO	12.5	6.7	12.4	DILS 14 GB LO	12.5	11.7	20.0
DILS 14 GA LO			20.0	DILS 16 GB LO			22.6
DILS 16 GA LO			22.6	DILS 18 GB LO			25.2
DILS 18 GA LO			25.2	DILS 24 GB LO			32.8
DILS 24 GA LO	20.1		32.8	DILS 28 GB LO	20.1		37.8
DILS 40 GA LO			53.1	DILS 40 GB LO			53.1
DILS 08 GB LO	12.5	11.7	12.4				

High-precision sockets and plugs for DIL-IC


SMD-plug for DIL

- with **SK 5**-contacts
- other number of contacts on request!

											
art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
DIL 08 SMD SK5 Z	8	7.62	10.1	3.5	10.0	DIL 20 SMD SK5 Z	20	7.62	10.1	3.5	25.2
DIL 16 SMD SK5 Z	16				20.1						
surface of contact:		tin-plated									

SMD-socket for DIL-IC

- other number of contacts upon request!


											
art. no.	no. of contacts	dim. [mm]				art. no.	no. of contacts	dim. [mm]			
DIL 16 SMD M	16	20.1	10.1	7.62	3.5	DIL 24 03 SMD M	24	30.3	10.1	7.62	3.5
DIL 20 SMD M	20	25.2				DIL 28 SMD M	28	35.4	17.6	15.24	11.2
contact spring:			gold-plated								
contact sleeve:			tin-plated								

IC-mounting tools - Design DIL

								
art. no.			spacing of contact rows [mm]					
MIC 03			7.62					
MIC 06			15.24					
material:			polyacetole, non-conductive					


Sockets for IC-PLCC

- PLCC sockets for case design EIA/JEDEC TYPE "A"
- **VPE** = packing unit (pieces/tube)
- data sheet for pin configuration of individual PLCC sockets available upon request
- dual polarity indicators guarantee the correct alignment of the chip
- drainage holes for easier inside cleaning
- test holes are moulded next to each contact

									
	art. no.	no. of contacts	packing unit	dim. [mm]					
				A 1	A 2	B 1	B 2	C	Ø D1
PLCC 20	20	39		5.08	5.08	15.55	15.55	16.7	10.16
PLCC 28	28	33		7.62	7.62	18.10	18.10	20.3	12.70
PLCC 32	32	29			10.16		20.70		15.24
PLCC 44	44	25		12.70	12.70	23.20	23.20	27.5	17.78
PLCC 52	52	23		15.24	15.24	25.70	25.70	31.0	20.32
PLCC 68	68	19		20.32	20.32	30.80	30.80	37.3	25.40
PLCC 84	84	16		25.40	25.40	36.00	36.00	44.5	30.48
surface of contact:			tin-plated						













SMD sockets for PLCC - low profile housing

- these PLCC sockets conform to case designs EIA/JEDEC TYPE "A"
- **VPE** = packing unit (pieces/tube)*dimensions ± 0.2 mm; tin-plated phosphorbronze socket contacts
- dual polarity indicators guarantee the correct alignment of the chip
- drainage holes for easier inside cleaning
- test holes are moulded next to each contact
- efficient heat dissipation
- **packing:** bar magazine

							
	art. no.	no. of contacts	packing unit	dim. [mm]			
				A	B	C	Q
PLCC 20 SMD	20	39		15.58	15.58	5.08	16.0
PLCC 28 SMD	28	33		18.12	18.12	7.62	20.6
PLCC 32 SMD	32	29			20.66		22.5
PLCC 44 SMD	44	26		23.40	23.40	12.70	27.5
PLCC 52 SMD	52	23		25.74	25.74	15.24	31.1
PLCC 68 SMD	68	20		30.82	30.82	20.32	38.8
PLCC 84 SMD	84	17		35.90	35.90	25.40	44.8
surface of contact:			tin-plated				


Sockets for TO ... cases

Transistor sockets for TO 5


			
art. no.	no. of contacts		
PF 53 ...	3		
			
art. no.	no. of contacts		
PF 54 ...	4		
			
art. no.	no. of contacts		
PF 58 23 ...	8		
please indicate:	... surface of contact G = gold-plated Z = tin-plated		
contact spring:	gold-plated		
			
art. no.	no. of contacts		
PF 58 2 G	8		
contact spring:	gold-plated		
contact sleeve:	gold-plated		

Sockets for TO ... cases

Sockets for TO 5






	
art. no.	no. of contacts
PF 510 G	10
contact spring:	gold-plated
contact sleeve:	gold-plated

Sockets for power transistors TO 3



	
art. no.	no. of contacts
TF 3 2	3
surface of contact:	gold-plated

Sockets for TO ... cases



Transistor sockets - teflon sockets for TO 5

			
art. no.	no. of contacts	art. no.	no. of contacts
TF 53	3	TF 54	4
			
art. no.	no. of contacts	art. no.	no. of contacts
TF 56	6	TF 58	8
			
art. no.	no. of contacts		
TF 510	10		







Transistor sockets - teflon sockets for TO 18

			
art. no.	no. of contacts	art. no.	no. of contacts
TF 183	3	TF 184	4
contact spring:	gold-plated		
contact sleeve:	gold-plated		

Sockets for crystal oscillators


art. no.			
QS 25 GS			
surface of contact:		silver-plated	

Precision sockets for crystal oscillators in case HC 18

art. no.				
PQ 18 ...				
art. no.				
PQ 18 W ...				
please indicate: ... surface of contact G = gold-plated Z = tin-plated				
contact spring:		gold-plated		



Insulators for crystal oscillators

* = equates self retaining


			
art. no.	case design	dim. [mm]	
ISQ 04	HC-18/U/ HC-49/U/ HC-43/U	C	D
ISQ 05		-	0.71
ISQ 06		-	*
ISQ 07		2.4	0.71
ISQ 08	HC-50/U/ HC-42/U/ HC-25/U	-	1.30
dielectric strength:		9 kV	
name of foil:		MYLAR	
heat resistance:		250°C	
material thickness:		0.127 mm	

Jumper links / Separable jumpers





Jumper links





art. no.	dim. [mm]		art. no.	dim. [mm]	
	A	B		A	B
LB 02 G	5.08	2.0	LB 04 G	10.16	7.0
LB 03 G	7.62	4.5	LB 06 G	15.24	12.0
surface of contact:		gold-plated			



art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A
CB 1 ...	2.54	CB 6 G	7.62
CB 3 ...	5.08		
please indicate: ... surface of contact G = gold-plated Z = tin-plated			



art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A
LEB 01 G	2.54	LEB 03 G	7.62
LEB 02 G	5.08		
surface of contact:		gold-plated	






art. no.
PSB 03 G
surface of contact:
gold-plated

Jumper links / Separable jumpers





Separable jumpers for soldering technology

– the contacts have a preformed dividing groove and can easily be separated with a screwdriver

							
art. no.	no. of contacts	dim. [mm]		art. no.	no. of contacts	dim. [mm]	
		A	B			A	B
CAB 3 06 03 Z	6	7.30	5.08	CAB 3 14 03 Z	14	17.46	15.24
CAB 3 08 03 Z	8	9.84	7.62	CAB 3 16 03 Z	16	20.00	17.78
CAB 3 12 03 Z	12	14.92	12.70				
surface of contact:		tin-plated					





Jumper links, grid spacing 2.54 mm, □ 0.635 mm

– **separable!** any requested number of contact can be delivered

						
art. no.	dim. [mm]		art. no.	dim. [mm]		
	A	C		A	C	
LB SL 0508 ...	5.08	6.1	LB SL 1016 ...	10.16	6.1	
LB SL 0762 ...	7.62		LB SL 1524 ...	15.24		
please indicate:						
... no. of contacts		... surface of contact				
1 - 36		G = gold-plated				
		Z = tin-plated				

Jumper links, grid spacing 2.00 mm, □ 0.5 mm


– **separable!** any requested number of contact can be delivered

						
art. no.	dim. [mm]					
	A		C			
LB SLY 06 ...	6		4.5			
please indicate:	... no. of contacts 1 - 50		... surface of contact G = gold-plated Z = tin-plated			

Jumper links / Separable jumpers











Jumper link for LED- and standard-PCBs

- in SMD-technology
- $\square$ 0,635 mm
- **separable!** any requested number of contact can be delivered



	
art. no.	
LB SL LP 039 SMD ...	
please indicate: ... no. of contacts 2 - 20 ... surface of contact G = gold-plated Z = tin-plated	

High-precision contacts, loose

Female contacts for Ø 0.5 mm

art. no.		art. no.		art. no.	
1706 G		PEK G		PK 1 ...	
art. no.		art. no.		art. no.	
1831 Z		WWPS 1 G		SK 06 ...	
art. no.		art. no.		art. no.	
SK 13 X 2 G		TF G		SK 19 ...	
art. no.					
SIL 1 ...					
contact spring:		gold-plated			
surface of contact:		gold-plated/ tin-plated			

Female contact for 0.64 mm □ and Ø 0.80 mm

art. no.		art. no.	
SKB 5 Z		SKB 9 Z	
contact spring:		gold-plated	
contact sleeve:		tin-plated	

High-precision contacts, loose

Contacts with solder head


art. no.		art. no.		art. no.	
PK 4 Z		SK 02 ...		SK 03 ...	
art. no.		art. no.			
SK 04 Z		SK 08 G			
please indicate: ... surface of contact G = gold-plated Z = tin-plated					

Pin contacts


art. no.		art. no.		art. no.	
SK 05 ...		SK 11 ...		SK 14 X 2 ...	
art. no.		art. no.		art. no.	
SK 40 G		SK 41 ...		SK 42 ...	
please indicate: ... surface of contact G = gold-plated Z = tin-plated					

Connector-sleeves


For 0.4 mm with BeCu spring 3 µm Ni, 0.1 µm Au

art. no.		
SB 1		




For 0.4 mm with bronze spring, teflon insulated

art. no.		
SB 2		

For 0.8 mm, slotted


art. no.		
SB 3		

For 1 mm, slotted


art. no.		
SB 4		
art. no.		
SB 5		
art. no.		
SB 6		
surface of contact:		gold-plated

Connector-sleeves


For 1 mm, slotted, plastic insulated

art. no.		
SB 9		


For 1 mm, with BeCu spring 3 µm Ni, 1 µm Au

art. no.		
SB 12		


For 1 mm, slotted, plastic insulated

art. no.		
SB 16		

For 2 mm, slotted, plastic insulated

art. no.		
SB 13 ...		
please indicate: ... case colour S = black R = red B = blue		

For 2 mm, slotted, plastic insulated, separable

art. no.		
SB 15		
surface of contact: gold-plated		

Single precision contacts
Teflon sockets/TO 5 & TO 18

High-precision female headers THT
Jumper links

→ F 17 – 18

→ F 12

→ G 2 – 6

→ F 14 – 16

Sockets für PLCC

Sockets for LED

Sockets for crystal oscillators

Technical data

→ F 9

→ F 5 – 6

→ F 13

→ F 21 – 26

Technical data: Sockets

	DIL ... E ..., DIL ... M ..., DIL ... N ..., DIL ... OR ...	DIL ... O ..., DIL ... P ..., DIL ... Q ..., DIL ... U ...	DIL ... PEK	DIL ... 06 E Z, DIL ... 06 H Z
contact material	CuZn-alloy			
surface contact / contact sleeve	Ni+≥0.2μm Au/ Ni+4...6μm Sn		Ni+≥0.2μm Au	Ni+4...6μm Sn
inner contact spring material	CuBe-alloy		CuBe-alloy	
inner contact spring surface	Ni+0,25μm Au		Ni+0,75μm Au	Ni+0,25μm Au
plugability for circuit points	0,22x0,25mm... 0,4x0,55mm/ Ø0,4...0,56mm		Ø0,4...0,56mm/ 0,22x0,25mm... 0,4x0,55mm	
insert depth	2.5...3.6mm		2.5...3.6mm	
insertion / drawing force	4 lamellas contact/ 1.8 N/1.4 N		4 lamellas contact/ 1.8 N/1.4 N	
shock resistance	50 g			
vibration resistance max.	15 g			
volume resistance	10 mΩ			
contact resistance	4 mΩ			
contact resistance after 1000 cycles	7 mΩ			
capacity between two adjacent con- tacts	0,4 pF			
nominal current	1.5 A			
nominal voltage	150 V DC			
test voltage	1000 V			
insulating body material	PPS, GF			
temperature range	-40°C... +200°C/ (260°C/10 s)			
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ¹² Ω·m			

Technical data: Sockets

	DIL ... G ..., DIL 14 W 90	DILS ... PK ...	DILS ... GO	DILS ... LO
contact material	CuZn-alloy		CuSn alloy	
surface contact / contact sleeve	Ni+4...6µm Sn	Ni+≥0.2µm Au		
inner contact spring material	CuBe-alloy			
inner contact spring surface	Ni+0,75µm Au			
plugability for circuit points	0,22x0,25mm... 0,4x0,55mm/ Ø0,4...0,56mm			
insert depth	2.5...3.6mm			
insertion / drawing force	4 lamellas contact/ 1.8 N/1.4 N			
shock resistance	50 g			
vibration resistance max.	15 g			
volume resistance	10 mΩ			
contact resistance	4 mΩ			
contact resistance after 1000 cycles	7 mΩ			
capacity between two adjacent con- tacts	0,4 pF			
nominal current	1.5 A			
nominal voltage	150 V DC			
test voltage	1000 V			
insulating body material	PPS, GF			PA 4.6. GF
temperature range	-40°C... +200°C/ (260°C/10 s)			-40°C... +163°C/ (260°C/10 s)
class of inflammability	UL 94 V-0			
specific insulation resistance	> 10 ¹² Ω·m			

Technical data: Sockets

	DIL ... SMD M, DIL...SMD SK5	MIC ...	PLCC ..., PLCC ... SMD	PF ..., PQ 18 ...
contact material	CuZn-alloy		CuSn alloy	CuZn-alloy
surface contact / contact sleeve	Ni+≥0.2μm Au/ Ni +4...6μm Sn		Ni+2...4μm Sn	Ni+≥0.2μm Au/ Ni +4...6μm Sn
inner contact spring material	CuBe-alloy			CuBe-alloy
inner contact spring surface	Ni+0,25μm Au			Ni+0,75μm Au
plugability for circuit points	0,22x0,25mm... 0,4x0,55mm/ Ø0,4...0,56mm			0,22x0,25mm... 0,4x0,55mm/ Ø0,4...0,56mm
insert depth	2.5...3.6mm			2.5...3.6mm
insertion / drawing force	4 lamellas contact/ 1.8 N/1.4 N			4 lamellas contact/ 1.8 N/1.4 N
shock resistance	50 g			50 g
vibration resistance max.	15 g			15 g
volume resistance	10 mΩ		>30 mΩ	10 mΩ
contact resistance				4 mΩ
contact resistance after 1000 cycles				7 mΩ
capacity between two adjacent con- tacts	0,4 pF			0,4 pF
nominal current	1.5 A		1 A	1.5 A
nominal voltage	150 V DC			60 V DC
test voltage	1000 V		500 V	
insulating body material	PPS, GF	polyacetal/ non-con- ductive	PPS, GF	PA 4.6. GF
temperature range	-40°C... +200°C/ (260°C/10 s)		-40°C... +105°C/ (260°C/10 s)	-40°C... +163°C/ (260°C/10 s)
class of inflammability	UL 94 V-0	UL 94 V-0 (at thickness ≥3mm), UL 94 V-1	UL 94 V-0	
specific insulation resistance	>10 ¹² Ω·m		>10 ⁸ Ω·m	>10 ⁷ Ω·m
	TF 3 2 (TO 3)	QS 25 GS	LB ... G	CB ...
contact material	CuSn-alloy, CuSn 6; Ni 1-2μm, Au 0.2μm	CuSn alloy	CuZn-alloy	
surface contact / contact sleeve		Ni+3μm Ag	Ni+≥0.2μm Au	Ni+≥0.2μm Au/ Ni +4...6μm Sn
volume resistance		10 mΩ		
contact resistance	<10 mΩ			
contact resistance after 1000 cycles		7 mΩ		
capacity between two adjacent con- tacts	1 pF			
nominal current		2.5 A		
nominal voltage		125 V DC		
test voltage	1650 V	500 V		
insulating body material	stanyl PA 4.6	PA, GF		
temperature range	-65°C ... +290°C	-40°C ... +180°C		
class of inflammability	UL 94 V-1	UL 94 V-0		
specific insulation resistance	>10 ⁷ Ω·m			
current rating	15 A max.			

Technical data: Sockets


	LEB ... G	PSB 03 G	CAB 3 ... 03 Z	LB SL ..., LB SL LP ...
contact material	CuZn-alloy	phosphor bronze	brass	CuSn alloy
surface contact / contact sleeve	Ni+0.15µm Au	Ni+≥0.2µm Au	Ni+4...6µm Sn	Ni+4...6µm Sn/ Ni+≥0.2µm Au
volume resistance				5 mΩ
nominal current	3 A		1.5 A	3 A
nominal voltage	150 V DC	125 V AC	100 V DC	250 V DC
test voltage	1000 V		1000 V	2000 V
insulating body material	thermoplastic polyester	PA 6. GF	PPS, GF	PA 4.6. GF
temperature range	-55°C... +125°C		-40°C... +200°C/ (260°C/10 s)	-40°C... +163°C/ (260°C/10 s)
class of inflammability	UL 94 V-0		UL 94 V-0	
specific insulation resistance			>10 ¹² Ω·m	>10 ⁷ Ω·m
	LB SLY 06 ...	1706 G, PEK G, WWPS 1 G	PK 1 ..., SK 19 ...	1831 Z, SIL 1 ..., SK 06 ..., SK 13 X 2 G
contact material	CuSn alloy	CuZn-alloy		
surface contact / contact sleeve	Ni+4...6µm Sn/ Ni+≥0.2µm Au	Ni+≥0.2µm Au	Ni+≥0.2µm Au/ Ni+4...6µm Sn	
inner contact spring material		CuBe-alloy		
inner contact spring surface		Ni+0,75µm Au	Ni+0,25µm Au	Ni+0,75µm Au
insert depth		2.5...3.6mm		
insertion / drawing force		4 lamellas contact/ 1.8 N/1.4 N		
volume resistance	5 mΩ			
nominal current	3 A	1.5 A		
nominal voltage	100 V DC	60 V DC		
test voltage	500 V	1000 V		
insulating body material	PA 4.6. GF			
temperature range	-40°C... +163°C/ (260°C/10 s)			
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ⁷ Ω·m			

Technical data: Sockets

	TF ..., TF G	SKB 5 Z, SKB 9 Z	PK 4 Z, SK 02 ..., SK 03 ..., SK 04 Z, SK 05 ..., SK 08 G, SK 14 X 2 ..., SK 40 G, SK 41 ..., SK 42 ...	SB 1
contact material	CuZn-alloy			
surface contact / contact sleeve	Ni+≥0.2μm Au	Ni+4...6μm Sn	Ni+≥0.2μm Au/ Ni +4...6μm Sn	Ni+≥0,1μm Au
inner contact spring material	CuBe-alloy			CuBe-alloy
inner contact spring surface	Ni+0,75μm Au			Ni+≥0,1μm Au
plugability for circuit points	Ø0,4...0,56mm/ 0,22x0,25mm... 0,4x0,55mm			Ø0,35...0,5 mm
insert depth	2.5...3.6mm	2.5...6mm		1.5...3mm
insertion / drawing force	4 lamellas contact/ 1.8 N/1.4 N	6 lamella contacts/ 1.3N/0.3N		
shock resistance	50 g			
vibration resistance max.	15 g			
volume resistance	10 mΩ			
contact resistance	4 mΩ			
contact resistance after 1000 cycles	7 mΩ			
nominal current	1.5 A	3 A	1.5 A	2 A
nominal voltage	100 V DC	150 V DC	60 V DC	
test voltage	1000 V			
insulating body material	PTFE			
temperature range	-200°C ... +260°C			
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ¹⁴ Ω·m			


Technical data: Sockets

	SB 2	SB 3	SB 4, SB 5, SB 6	SB 9
contact material	CuZn-alloy			
surface contact / contact sleeve	Ni+ $\geq 0.2\mu\text{m Au}$	Ni+ $0.25\mu\text{m Au}$		
inner contact spring material	CuBe-alloy			
inner contact spring surface	Ni+ $0,75\mu\text{m Au}$			
plugability for circuit points	$\varnothing 0,4 \dots 0,56\text{mm} / 0,22 \times 0,25\text{mm} \dots 0,4 \times 0,55\text{mm}$	$\varnothing 0,8\text{mm}$	$\varnothing 1\text{mm}$	
insert depth	2.8...3.8mm	4mm	6mm	
nominal current	2 A		3 A	
nominal current 70°C	1 A		2 A	
insulating body material	PTFE (teflon)			PA 6.6
dielectric strength	$\leq 500\text{ V}$		$\leq 500\text{ V}$	
	SB 12	SB 16	SB 13	SB 15
contact material	CuZn-alloy			
surface contact / contact sleeve	Ni+ $0.25\mu\text{m Au}$			
inner contact spring material	CuBe-alloy			
inner contact spring surface	Ni+ $1\mu\text{m Au}$			
plugability for circuit points	$\varnothing 1\text{mm}$		$\varnothing 2\text{mm}$	
insert depth	3.8...5.5mm	2...6mm	6mm	12mm
volume resistance	$> 30\ \Omega$			
nominal current	4 A		3 A	
nominal current 70°C			2 A	
insulating body material		PBT, GF	polyolefin	PA 4.6. GF
class of inflammability		UL 94 V-0		UL 94 V-0
dielectric strength			$\leq 500\text{ V}$	




Male and female headers in SMD version

- male header, one and two rows with pick and place pad, horizontal and vertical version
- female header, one and two rows with pick and place pad, horizontal and vertical version
- grid spacing: 2,54 mm, 2,00 mm and 1,27 mm
- optional selectable type of packaging: bar magazine and tape and reel




Male and female headers for solder technology (THT)

- male header, one and two rows, straight and angled version with square and precision contacts
- shrouded-header with second insulating body
- female header, one and two rows, straight and angled version with stamped contacts or precision contacts
- through-hole female headers, one and two rows
- grid spacing 2,54 mm, 2,0 mm and 1,27 mm



Male and female header in press-in mounting

- male header, one and two rows, straight version
- female header, one and two rows, straight version
- shrouded male header, two rows, straight version



Multipoint connector

- direct multipoint connector for additional circuit board with a thickness of 0,7 to 0,9 mm
- direct multipoint connector for a circuit board thickness of 1,6 mm

Male headers

Präzisionskontakte, solder and plug pins Ø 0.5 mm

– also available as single contact, **SK ...** → F 18

– **version:**

MK 05 / MK 205: contact pin on both sides

MK 04 / MK 204: solder-cup

MK 03 / MK 203: with solder head

MK 02 / MK 202: with solder fork

art. no.			art. no.		
MK 05 ...			MK 205 ...		
MK 04 ...			MK 204 ...		
MK 03 ...			MK 203 ...		
MK 02 ...			MK 202 ...		
please indicate: ... no. of contacts one row 1 - 50 two rows 2 - 100 ... surface of contact G = gold-plated Z = tin-plated					





Male headers

Precision contacts, Wire Wrap pin □ 0.635 mm

– version:

MK 10 / MK 210: with solder-cup




MK 08 / MK 208: with solder fork

art. no.			art. no.		
MK 10 ...			MK 210 ...		
art. no.			art. no.		
MK 08 ...			MK 208 ...		
please indicate:					
... no. of contacts		... surface of contact			
one row 1 - 50		G = gold-plated			
two rows 2 - 100		Z = tin-plated			



Male headers

Precision contacts, solder and plug pins, Ø 0.5 mm

– rectangular PCB connection

art. no.			art. no.		
MK 51 ...			MK 251 ...		
art. no.					
MK 15 ...					
please indicate:					
... no. of contacts		... surface of contact			
one row 1 - 50		G = gold-plated			
two rows 2 - 100		Z = tin-plated			








– parallel PCB connection

						
art. no.	dim. [mm]		art. no.	dim. [mm]		
	A	X		A	B	X
	MK 14 X 1 ... G	13.42.7		MK 214 X 1 ... G	13.41.9	2.7
	MK 14 X 2 ... G	15.44.7		MK 214 X 2 ... G	15.43.9	4.7
MK 14 X 3 ...	22.211.7	MK 214 X 3 ...	22.210.9	11.7		
please indicate:						
... no. of contacts			... surface of contact			
one row 1 - 50			G = gold-plated			
two rows 2 - 100			Z = tin-plated			

Male headers

Precision contacts, low profile




– also available as single contact, **SK ...** → F 18

art. no.			art. no.		
MK LP 40 ...			MK LP 240 ...		
art. no.			art. no.		
MK LP 41 ...			MK LP 241 ...		
art. no.			art. no.		
MK LP 42 ...			MK LP 242 ...		
art. no.					
MK LP 43 ...					
please indicate:					
... no. of contacts		... surface of contact			
one row 1 - 50		G = gold-plated			
two rows 4 - 100		Z = tin-plated			

Male headers


Precision contacts, low profile

- one row

art. no.		
SL 7 ...		
art. no.		
SL 8 ...		
art. no.		
SL 9 ...		
please indicate: ... no. of contacts one row 1 - 20 ... surface of contact G = gold-plated Z = tin-plated		




Male headers

- every pin length is available on request
- one row, □ 0.635 mm

									
art. no.	dim. [mm]				art. no.	dim. [mm]			
	A	B	C	S		A	B	C	S
SL 11 097...	9.7	3.0	3.9	4	SL 1 025 ...	11.2	5.8	5.8	4
SL 11 112 ...	11.2		5.4		SL 1 053 ...	13.9		5.3	
SL 11 124 ...	12.4		6.6	5	SL 1 078 ...	16.4		7.8	5
SL 11 139 ...	13.9		8.1		SL 1 104 ...	19.0		10.4	
SL 11 164 ...	16.4		10.6		SL 1 128 ...	21.4		12.8	6
SL 11 190 ...	19.0		13.2		SL 1 154 ...	24.0		15.4	
SL 11 214 ...	21.4		15.6	6	SL 1 179 ...	26.5		17.9	
SL 11 240 ...	24.0		18.2		SL 1 230 ...	31.6		23.0	
SL 11 265 ...	26.5		20.7						
SL 11 316 ...	31.6		25.8						
please indicate: ... no. of contacts one row 1 - 36 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated									

Male headers

- every pin length is available on request
- two rows, $\square$ 0.635 mm



art. no.	dim. [mm]				art. no.	dim. [mm]			
	A	B	C	S		A	B	C	S
SL 22 097 ...	9.7	3.0	3.9	4	SL 2 025 ...	11.2	5.8	5.8	4
SL 22 112 ...	11.2		5.4		SL 2 053 ...	13.9		5.3	
SL 22 124 ...	12.4		6.6	5	SL 2 078 ...	16.4		7.8	5
SL 22 139 ...	13.9		8.1		SL 2 104 ...	19.0		10.4	
SL 22 164 ...	16.4		10.6		SL 2 128 ...	21.4		12.8	6
SL 22 190 ...	19.0		13.2	SL 2 154 ...	24.0	15.4			
SL 22 214 ...	21.4		15.6	SL 2 179 ...	26.5	17.9			
SL 22 240 ...	24.0		18.2	SL 2 230 ...	31.6	23.0			
SL 22 265 ...	26.5		20.7						
SL 22 316 ...	31.6		25.8						

please indicate:

... no. of contacts

two rows 2 - 72

... surface of contact

S = selective gold-plated

G = gold-plated




Z = tin-plated

Male headers





Through-Hole-Reflow (THR) soldering technology

– every pin length is available upon request

– one row, $\square$ 0.635 mm

												
art. no.	dim. [mm]				art. no.	dim. [mm]						
	A	B	C	S		A	B	C	S			
SL 20 THR 097 ...	9.7	2	4.9	4	SL 20 THR 139 ...	13.9	2	9.1	5			
SL 20 THR 112 ...	11.2		6.4		SL 20 THR 164 ...	16.4		11.6				
SL 20 THR 124 ...	12.4		7.6	5								
please indicate:												
... no. of contacts one row 1 - 36					... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated							

– two rows, $\square$ 0.635 mm

	  								
art. no.	dim. [mm]				art. no.	dim. [mm]			
	A	B	C	S		A	B	C	S
SL 21 THR 097 ...	9.7	2	4.9	4	SL 21 THR 139 ...	13.9	2	9.1	5
SL 21 THR 112 ...	11.2		6.4		SL 21 THR 164 ...	16.4		11.6	
SL 21 THR 124 ...	12.4		7.6	5					
please indicate: ... no. of contacts two rows 2 - 72 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated									




Male headers

"Dimensions A + B" changeable

- **separable!** any requested number of contact can be delivered
- any pin length is available upon request




– one row, □ 0.635 mm

– **the surface of dimension "C"** of following articles is selective gold-plated: **SLK 3 025 ... S, SL 3 025 ... S**

												
art. no.		dim. [mm]				art. no.		dim. [mm]				
		A	B	C	S			A	B	C	S	
SL 3 025 ...		4.5	3.0	5.8	5	SL 3 152 ...		16.7	15.2	5.8	6	
SL 3 053 ...		6.9	5.4			SL 3 182 ...		19.7	18.2			
SL 3 080 ...		9.5	8.0			SL 3 207 ...		22.2	20.7			
SL 3 101 ...		11.6	10.1	6	6	SLK 3 025 ...		4.5	3.0	3.0	4	
SL 3 131 ...		14.6	13.1									
please indicate:												
... no. of contacts				... surface of contact								
one row 1 - 36				S = selective gold-plated								
				G = gold-plated								
				Z = tin-plated								

– two rows, □ 0.635 mm

– **the surface of dimension "C"** of following articles is selective gold-plated: **SLK 4 025 ... S, SL 4 025 ... S**




												
art. no.	dim. [mm]				art. no.	dim. [mm]						
	A	B	C	S		A	B	C	S			
SL 4 025 ...	4.5	3.0	5.8	5	SL 4 152 ...	16.7	15.2	5.8	6			
SL 4 101 ...	11.6	10.1		6	SLK 4 025 ...	4.5	3.0	3.0	4			
please indicate:												
... no. of contacts					... surface of contact							
two rows 2 - 72					S = selective gold-plated							
					G = gold-plated							
					Z = tin-plated							

Male headers




Insertion side "dimension C" changeable

- **separable!** any requested number of contact can be delivered
- any pin length is available on request

– one row, □ 0.635 mm

						
art. no.	dim. [mm]		art. no.	dim. [mm]		
	C	S		C	S	
SL 18 042 ...	4.2	5	SL 18 108 ...	10.8	5	
SL 18 082 ...	8.2		SL 18 132 ...	13.2	6	
please indicate:	... no. of contacts one row 1 - 36		... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated			

– two rows, □ 0.635 mm



						
art. no.	dim. [mm]		art. no.	dim. [mm]		
	C	S		C	S	
SL 19 082 ...	8.2	5	SL 19 132 ...	13.2	6	
SL 19 108 ...	10.8					
please indicate:	... no. of contacts two rows 2 - 72		... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated			

Male headers


Low profile, straight

– any pin length is available on request

– one row, □ 0.635 mm

									
art. no.	dim. [mm]				art. no.	dim. [mm]			
	A	B	C	S		A	B	C	S
SL LP 1 082 ...	8.2	3	3.5	3	SL LP 1 139 ...	13.9	3	9.2	5
SL LP 1 097 ...	9.7		5.0	4	SL LP 1 164 ...	16.4		11.7	
SL LP 1 112 ...	11.2		6.5		SL LP 1 190 ...	19.0		14.3	
please indicate:									
... no. of contacts one row 1 - 36					... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated				

– two rows, □ 0.635 mm




									
art. no.	dim. [mm]				art. no.	dim. [mm]			
	A	B	C	S		A	B	C	S
SL LP 2 082 ...	8.2	3	3.5	3	SL LP 2 139 ...	13.9	3	9.2	5
SL LP 2 097 ...	9.7		5.0	4	SL LP 2 164 ...	16.4		11.7	
SL LP 2 112 ...	11.2		6.5		SL LP 2 190 ...	19.0		14.3	
please indicate:	... no. of contacts two rows 2 - 72 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated								

Male headers




Low profile, angled

– any pin length is available on request

– one row, $\square$ 0.635 mm

																			
art. no.					dim. [mm]					art. no.					dim. [mm]				
					A	B	C	S							A	B	C	S	
SL LP 3 041 ...					4.5	3	4.1	4		SL LP 3 069 ...					4.5	3	6.9	5	
please indicate:					... no. of contacts					... surface of contact									
					one row 1 - 36					S = selective gold-plated									
										G = gold-plated									
										Z = tin-plated									

– two rows, $\square$ 0.635 mm




																			
art. no.					dim. [mm]					art. no.					dim. [mm]				
					A	B	C								A	B	C	S	
SL LP 4 041 ... G					4.5	3	4.1			SL LP 4 069 ...					4.5	3	6.9	5	
SL LP 4 041 ... Z																			
please indicate:					... no. of contacts					... surface of contact									
					two rows 2 - 72					S = selective gold-plated									
										G = gold-plated									
										Z = tin-plated									

Male headers




Sandwich-design

- "S" selective gold-plated up to 33 mm pin length
- for interconnections of stacked PCBs
- within the total length of the pin the insulator position can be changed as required ... **Design specification-sheet**
- **separable!** any requested number of contact can be delivered

– one row, □ 0,635 mm

										
art. no.	dim. [mm]			art. no.	dim. [mm]			art. no.	dim. [mm]	
	A	L	S		A	L	S		A	L
SL 5 071 ...	7.1	16.4	5	SL 5 156 Z	15.6	24.9	6	SL 5 285 ...	28.5	37.8
SL 5 097 ...	9.7	19.0		SL 5 172 ...	17.2	26.5		SL 5 315 ...	31.5	40.8
SL 5 121 ...	12.1	21.4	6	SL 5 197 ...	19.7	29.0	6	SL 5 360 ...	36.0	45.3
SL 5 147 ...	14.7	24.0		SL 5 223 ...	22.3	31.6		SL 5 415 ...	41.5	50.8
SL 5 156 G	15.6	24.9		SL 5 237 ...	23.7	33.0		SL 5 525 ...	52.2	61.5
please indicate:										
... no. of contacts										
one row 1 - 36										
... surface of contact										
S = selective gold-plated										
G = gold-plated										
Z = tin-plated										

– two rows, □ 0,635 mm

										
art. no.	dim. [mm]			art. no.	dim. [mm]			art. no.	dim. [mm]	
	A	L	S		A	L	S		A	L
SL 6 071 ...	7.1	16.4	5	SL 6 156 Z	15.6	24.9	6	SL 6 285 ...	28.5	37.8
SL 6 097 ...	9.7	19.0		SL 6 172 ...	17.2	26.5		SL 6 315 ...	31.5	40.8
SL 6 121 ...	12.1	21.4	6	SL 6 197 ...	19.7	29.0	6	SL 6 360 ...	36.0	45.3
SL 6 147 ...	14.7	24.0		SL 6 223 ...	22.3	31.6		SL 6 415 ...	41.5	50.8
SL 6 156 G	15.6	24.9		SL 6 237 ...	23.7	33.0		SL 6 525 ...	52.2	61.5
please indicate:										
... no. of contacts										
two rows 2 - 72										
... surface of contact										
S = selective gold-plated										
G = gold-plated										
Z = tin-plated										

Female headers 2.54 THT

High-prec. male headers 2.54 THT

Female headers for PC 104

Male headers, sandwich-design 2.00

→ G 65

→ G 58 – 68

→ G 68 – 69

→ G 40

Jumpers

Female headers 2.54 SMD

Female headers 2.54

Technical data

→ G 100 – 101

→ G 73 – 78

→ G 63 – 81

→ G 102 – 108




G 14

Male headers

Sandwich-design

- **"S" selective gold-plated up to 33 mm pin length**
- for interconnections of stacked PCBs
- for plugging the the female headers **BL 11 (SL 13 ...)** → G 65 and **BL 12 (SL 14 ...)** → G 65
- suitable for PCB thicknesses between 1.5 mm and 33 mm
- **separable!** any requested number of contact can be delivered

– one row □ 0.635 mm

							
art. no.	dim. [mm]			art. no.	dim. [mm]		
	A	L	S		A	L	
SL 13 071 ...	7.1	21.4	6	SL 13 235 ...	23.5	37.8	
SL 13 097 ...	9.7	24.0		SL 13 265 ...	26.5	40.8	
SL 13 122 ...	12.2	26.5		SL 13 310 ...	31.0	45.3	
SL 13 147 ...	14.7	29.0		SL 13 365 ...	36.5	50.8	
SL 13 187 ...	18.7	33.0					
please indicate:	... no. of contacts one row 1 - 36			... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated			

- two rows, $\square$ 0.635 mm

date: _____
 pieces per order: _____
 company: _____
 name, dept.: _____
 town: _____
 street: _____
 fax: _____
 signature: _____


- ☐ inquiry
☐ order

surface finish

- ☐ selective gold-plated
☐ gold-plated
☐ tin-plated

- ☐ one row 1 - 36 contacts possible
☐ two rows 2 - 72 contacts possible

number of contacts

dimensions:


L = total contact length
A = distance between PCBs
B = solder side
C = insertion side

L

A




B

C

Male headers

Shrouded male header, with coding and bolting device

– suitable for many flat cable connectors in 2.54 mm pitch

	  						
art. no.	no. of con- tacts	dim. [mm]					
		A	B	C	D	E	S
SLU 10 165 ...	10	20.4	17.8	10.16	13.5	16.5	5
SLU 10 191 ...					16.1	19.1	
SLU 10 241 ...					21.1	24.1	6
SLU 10 266 ...					23.6	26.6	
SLU 16 165 ...	16	28.0	25.4	17.78	13.5	16.5	5
SLU 16 191 ...					16.1	19.1	
SLU 16 241 ...					21.1	24.1	6
SLU 16 266 ...					23.6	26.6	
SLU 20 165 ...	20	33.1	30.5	22.86	13.5	16.5	5
SLU 20 191 ...					16.1	19.1	
SLU 20 241 ...					21.1	24.1	6
SLU 20 266 ...					23.6	26.6	
SLU 26 165 ...	26	40.7	38.1	30.48	13.5	16.5	5
SLU 26 191 ...					16.1	19.1	
SLU 26 241 ...					21.1	24.1	6
SLU 26 266 ...					23.6	26.6	
SLU 40 165 ...	40	58.5	55.9	48.26	13.5	16.5	5
SLU 40 191 ...					16.1	19.1	
SLU 40 241 ...					21.1	24.1	6
SLU 40 266 ...					23.6	26.6	
SLU 50 165 ...	50	71.2	68.6	60.96	13.5	16.5	5
SLU 50 191 ...					16.1	19.1	
SLU 50 241 ...					21.1	24.1	6
SLU 50 266 ...					23.6	26.6	
please indicate: ... surface of contact S = selective gold-plated Z = tin-plated							

Male headers


Three rows, □ 0.635 mm

art. no.	dim. [mm]			
	A	B	C	
SL KG 3 113 ...	11.3	3.3	5.5	
SL KG 3 126 ...	12.6		6.8	
SL KG 3 147 ...	14.7		8.9	
art. no.	dim. [mm]			
	A	B	C	
SL KA 3 072 ...	7.2	3.3	3.4	
SL KA 3 085 ...	8.5		4.7	
SL KA 3 108 ...	10.8		7.0	
please indicate: ... no. of contacts ... surface of contact three rows 3 - 150 G = gold-plated Z = tin-plated				

Male headers

Turned precision male contacts

- Suitable for **BL 22 SHK 14 02 G** → G 70 and **BL 23 SHK 14 02 SMD G** → G 76
- Signal and high-power contacts
- Contacts gold-plated
- Other number of contacts / contact surface upon request

					
art. no.			signal contacts		high-power contacts
SL 26 SHK 14 02 G			12		2
surface of contact:			gold-plated		

Male headers

Precision contacts, plug pins Ø 0.5 mm

art. no.			
MK 26 SMD ...			
please indicate:	... no. of contacts one row 4 - 20	... surface of contact G = gold-plated Z = tin-plated	... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (250pcs/reel)

... packing (option) - additions:
MK 26 SMD ... B TR: 4-12 contacts




Option, for automatic assembly

– reel diameter Ø 330 mm

... SM		MK 26 SMD ... SM	MK 26 SMD ... B SM
... B SM			
... B TR		MK 26 SMD ... B TR	

Male headers

Precision contacts, plug pins Ø 0.5 mm

art. no.						
MK 226 SMD ...						
please indicate:	... no. of contacts two rows 4 - 40	... surface of contact G = gold-plated Z = tin-plated		... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (250pcs/reel)		







... packing (option) - additions:

MK 226 SMD ... SM; ... B SM: 6-40 contacts

MK 226 SMD ... B TR: 6-24 contacts



Option, for automatic assembly

– reel diameter Ø 330 mm

			
... SM		MK 226 SMD ... SM	MK 226 SMD ... B SM
... B SM			
			
... B TR	MK 226 SMD ... B TR		


Male headers

Precision contacts, plug pins Ø 0.5 mm

art. no.			
MK 27 SMD ...			
please indicate:	... no. of contacts one row 2 - 20	... surface of contact G = gold-plated Z = tin-plated	... packing (optional) SM = bar magazine




... packing (option) - additions:
MK 27 SMD ... SM: 3-20 contacts

Option, for automatic assembly

	
... SM	MK 27 SMD ... SM

Male headers

□ 0.635 mm

								
art. no.	dim. [mm] C S		art. no.	dim. [mm] C S		art. no.	dim. [mm] C S	
SL 10 SMD 040 ...	4.0	4	SL 10 SMD 062 ...	6.7	5	SL 10 SMD 104 ...	10.8	5
SL 10 SMD 052 ...	5.5		SL 10 SMD 078 ...	8.2		SL 10 SMD 130 ...	13.4	
please indicate:								
... no. of contacts one row 4 - 20			... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated			... packing SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel		

... packing (option) - additions:

SL 10 SMD 040 - 104 ... SM; ... B SM: 4-20 contacts






SL 10 SMD 040 - 062 ... B TR: 4-20 contacts, 250 pcs/reel











SL 10 SMD 078 ... B TR: 4-12 contacts, 250 pcs/reel

SL 10 SMD 104 - 130 ... B TR: 4-12 contacts, 150 pcs/reel

Option, for automatic assembly



– reel diameter Ø 330 mm

												
... SM				SL 10 SMD ... SM			SL 10 SMD ... B SM					
... B SM												

												
	SL 10 SMD 040-062 ... 4-12 ... B TR							SL 10 SMD 040-062 ... 13-20 ... B TR				
												
	SL 10 SMD 078 ... 4-12 ... B TR							SL 10 SMD 104 - 130 ... 4-12 ... B TR				
... B TR												

Male headers

□ 0.635 mm

					
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
SL 11 SMD 040 ...	C 4.0	SL 11 SMD 062 ...	C 6.7	SL 11 SMD 104 ...	C 10.8
SL 11 SMD 052 ...	S 5.5	SL 11 SMD 078 ...	S 8.2	SL 11 SMD 130 ...	S 13.4
please indicate:		... no. of contacts		... surface of contact	
		two rows 4 - 40		S = selective gold-plated	
				G = gold-plated	
				Z = tin-plated	
				... packing (optional)	
				SM = bar magazine	
				B SM = pick and place pad and bar magazine	
				B TR = pick and place pad and tape and reel	

... packing (option) - additions:









SL 11 SMD 040-104 ... SM; ... B SM: 6-40 contacts

SL 11 SMD 040-078 ... B TR: 6-24 contacts, 250 pcs/reel

SL 11 SMD 104-130 ... B TR: 6-24 contacts, 150 pcs/reel

Option, for automatic assembly

– reel diameter Ø 330 mm

									
... SM						SL 11 SMD ... SM		SL 11 SMD ... B SM	
... B SM									
						SL 11 SMD 040-062 ... B TR		SL 11 SMD 078 ... B TR	
... B TR									
						SL 11 SMD 104-130 ... 6-24 ... B TR			

Female headers for PC 104
Jumpers
Female headers for PC 104
Direct female connectors

→ G 68 – 69
→ G 100 – 101
→ G 68 – 69
→ G 99

High-prec. male headers 2.54 THT
Female headers 2.54 THT
Female headers 2.54 SMD
Technical data

→ G 58 – 68
→ G 65
→ G 73 – 78
→ G 102 – 108

G 24

A

B

C

D

E

F

G

H

I

K





L

M

N

Male headers





□ 0.635 mm

	 S = 5 mm										
art. no.	dim. [mm]			art. no.	dim. [mm]			art. no.	dim. [mm]		
	B	C	S		B	C	S		B	C	S
SL 12 SMD 031 ...	5.2	3.1	4	SL 12 SMD 035 ...	3.2	3.5	4	SL 12 SMD 083 ...	5.2	8.3	5
SL 12 SMD 032 ...	3.2	5.8	—	SL 12 SMD 058 ...	5.2	5.8	5	SL 12 SMD 109 ...		10.9	
please indicate: ... no. of contacts one row 2 - 20 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated ... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (500pcs/reel)											

... packing (option) - additions:
SL 12 SMD ... B TR: 2-13 contacts



Option, for automatic assembly

— reel diameter Ø 330 mm

					
... B SM				SL 12 SMD ... B SM	
					
... B TR				SL 12 SMD 031-109 ... B TR	

Male headers





□ 0.635 mm

					
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	C		C S		C S
SL 17 SMD 058 ...	5.8	SL 17 SMD 083 ...	8.3 5	SL 17 SMD 109 ...	10.9 5
please indicate: ... no. of contacts two rows 4 - 40 ... surface of contact G = gold-plated Z = tin-plated ... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (300pcs/reel)					

... packing (option) - additions:
SL 17 SMD ... B TR: 6-24 contacts


Option, for automatic assembly

– reel diameter Ø 330 mm

		
... B SM	SL 17 SMD ... B SM	
		
... B TR	SL 17 SMD 058-109 ... B TR	

Male headers

Low profile in SMD □ 0.635 mm




... packing (option) - additions:

SL LP 5 SMD ... SM; ... B SM: 4-20 contacts

SL LP 5 SMD ... B TR: 4-20 contacts

Option, for automatic assembly

- reel diameter Ø 330 mm



Male headers

Low profile in SMD □ 0.635 mm

art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	C S		C S		C S
SL LP 6 SMD 038 ...	3.8 3	SL LP 6 SMD 051 ...	5.1 4	SL LP 6 SMD 066 ...	6.6 4
please indicate: ... no. of contacts two rows 4 - 40 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated ... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (250pcs/reel) ... positioning (optional) PS = locating pin (2 pcs/bar bigger than 6 contacts)					









... packing (option) - additions:

SL LP 6 SMD ... SM; ... B SM: 6-40 contacts

SL LP 6 SMD ... B TR: 6-24 contacts

Option, for automatic assembly

– reel diameter Ø 330 mm

				
... SM			SL LP 6 SMD ... SM	SL LP 6 SMD ... B SM PS
... B SM				
				
... B TR			SL LP 6 SMD 038-066 ... B TR	




Male headers

art. no.	dim. [mm]			
	A	B	C	S
SL LP 7 SMD 030 ...	8.0	3.3	3.0	3
SL LP 7 SMD 040 ...	9.5	3.8	4.0	4
SL LP 7 SMD 055 ...	11.0		5.5	
please indicate:	... no. of contacts 2 - 20			
	... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated			




Male headers

□ 0.635 mm – for interconnections of stacked PCBs

- one row, 4-20 contacts
- within the total length of the pin the insulator can be changed according to customer's request

							
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	A S		A S		A S		A S
SL 15 SMD 182 ...	18.2 6	SL 15 SMD 207 ...	20.7 6	SL 15 SMD 107 ...	10.7 5		
please indicate: ... no. of contacts one row 4 - 20 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated ... positioning (optional) P = end pins straight for positioning							

- two rows, 4-40 contacts
- within the total length of the insulator can be changed according to customer's request

							
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	A S		A S		A S		A S
SL 16 SMD 107 ...	10.7 5	SL 16 SMD 182 ...	18.2 6	SL 16 SMD 247 ...	24.7 6		
SL 16 SMD 157 ...	15.7 6	SL 16 SMD 207 ...	20.7 6				
please indicate: ... no. of contacts two rows 4 - 40 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated ... positioning (optional) P = end pins straight for positioning							

Male headers

Turned precision male contacts

- suitable for **BL 22 SHK 14 02 G** → G 70 and **BL 23 SHK 14 02 SMD G** → G 76
- signal and high-power contacts
- contacts gold-plated
- other number of contacts / contact surface upon request




art. no.	signal contacts	high-power contacts
SL 27 SHK 14 02 SMD G	12	2
surface of contact:	gold-plated	

Male headers




Male connectors in pressfit technology

- press-fit mounting without soldering, resilient press-fit area, easy insertion into the PCB
- Pressfit bar with insulating body has to be inserted up to the PCB
- **separable!** any requested number of contact can be delivered
- **contact material:** Cu Sn 6


- one row, 1-36 contacts
- for PCB thickness ≥ 1.6 mm dimension B = 3.5 mm and ≥ 3.0 mm dimension B = 4.5 mm

									
art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SLP 1 16 117 ...	11.7	3.5	5.4	SLP 1 16 144 ...	14.4	3.5	8.1		
SLP 1 16 129 ...	12.9		6.6	SLP 1 16 195 Z	19.5		13.2		
please indicate:									
... no. of contacts		... surface of contact							
one row 1 - 36		G = gold-plated							
		Z = tin-plated							

- two rows, 2-72 contacts
- for PCB thickness ≥ 1.6 mm dimension B = 3.5 mm and ≥ 3.0 mm dimension B = 4.5 mm

									
art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SLP 2 16 117 ...	11.7	3.5	5.4	SLP 2 16 144 ...	14.4	3.5	8.1		
SLP 2 16 129 ...	12.9		6.6	SLP 2 16 195 Z	19.5		13.2		
please indicate:									
... no. of contacts				... surface of contact					
two rows 2 - 72				G = gold-plated					
				Z = tin-plated					

Hole diameter in PCB - hole structure acc. to DIN EN 60352-5



Male headers 2.00 SMD
High-prec. male headers 1.27 SMD
Male headers 2.54 THT
Female headers 1.27 THT

→ G 43 – 45
→ G 56
→ G 7
→ G 94

Jumpers
High-prec. fem. headers 2.54 THT
Female headers 2.00 SMD
Technical data

→ G 100 – 101
→ G 66 – 69
→ G 90
→ G 102 – 108

G 32

A

B

C

D

E

F

G

H

I

K

L

M

N

Male headers

Male header with shroud in pressfit technology

- suitable for lockable female multipoint connector **VFL ...** → H 11 and can be combined with many other female multipoint connectors with grid spacing 2.54 mm (e. g.: **PV ...**, **BL ...**)
- press-fit mounting without soldering, resilient press-fit area, easy insertion into PCB
- Pressfit bar with insulating body has to be inserted up to the PCB
- **contact material:** Cu Sn 6

art. no.	no. of contacts	dim. [mm]				
		A	B	C	D	E
SLUP 31 10 ...	10	20.4	17.8	10.16	12.6	3.5
SLUP 31 16 ...	16	28.0	25.4	17.78		
SLUP 31 20 ...	20	33.1	30.5	22.86		
please indicate: ... surface of contact G = gold-plated Z = tin-plated						


Hole diameter in PCB - hole structure acc. to DIN EN 60352-5

--

Male headers

Male connectors for LED applications


- every pin length is available upon request
- insulating body made of white plastic (nature)
- one row, $\square$ 0.635 mm

				
art. no.	dim. [mm]			
	A	B	C	S
SL 24 LED 097 ...	9.7	3	3.9	4
SL 24 LED 112 ...	11.2		5.4	
SL 24 LED 124 ...	12.4		6.6	5
please indicate: ... no. of contacts one row 1 - 36 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated				

Male headers

Male connectors for LED applications

- every pin length is available upon request
- insulating body made of white plastic (nature)
- one row, $\square$ 0.635 mm

				
art. no.	dim. [mm]			
	A	B	C	S
SL 25 LED THR 097 ...	9.7	2	4.9	4
SL 25 LED THR 112 ...	11.2		6.4	
SL 25 LED THR 124 ...	12.4		7.6	5
please indicate:				
... no. of contacts one row 1 - 36		... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated		

Male headers

Male connectors for LED applications

- insulating body made of white plastic (nature)
- one row, $\square$ 0.635 mm

art. no.	dim. [mm] B C S
SL 23 LED SMD 031 ...	5.2 3.1 4
SL 23 LED SMD 058 ...	5.2 5.8 5
please indicate:	... no. of contacts one row 2 - 20 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated ... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (500pcs/reel)

... packing (option) - additions:

SL 23 LED ... B TR: 2-13 contacts



Option, for automatic assembly

... B SM	SL 23 LED SMD ... B SM
... B TR	SL 23 LED SMD ... B TR

Male headers

PCB connector for LED inline modules



- for SMD-soldering technology
- suitable for SMD soldering processes
- simple and save connection assembly
- long life-cycle due to advanced contact geometries and surfaces
- **type of packing: tape and reel (TR) 600 pcs. / tape**

	
art. no.	no. of contacts
SL 40 SMD 2 LED TR	2
	
art. no.	no. of contacts
SL 40 SMD 4 LED TR	4
surface of contact:	tin-plated
soldering section:	tin-plated
color plug housing:	white

Male headers

PCB connector for LED-inline modules

- for Through-Hole-Reflow (THR) soldering technology
- suitable for SMD soldering processes
- simple and save connection assembly
- long life-cycle due to advanced contact geometries and surfaces
- **type of packing: tape and reel (TR) 500 pcs. / tape**

	
art. no. SL 41 THR 2 LED TR	no. of contacts 2
	
art. no. SL 41 THR 4 LED TR	no. of contacts 4
surface of contact:	tin-plated
soldering section:	tin-plated
color plug housing:	white

Male headers

Standard, □ 0.5 mm

– any requested number of contact is available




art. no.	dim. [mm]				art. no.	dim. [mm]						
SLY 1 081 ...	A	B	C	S	SLY 1 104 ...	A	B	C	S			
SLY 1 085 ...	8.1	3	3.6	3.0	SLY 1 139 ...	10.4	3	5.9	3.5			
SLY 1 098 ...	8.5		4.0	3.5	13.9	9.4						
	9.8		5.3									
art. no.	dim. [mm]				art. no.	dim. [mm]						
SLY 2 081 ...	A	B	C	S	SLY 2 104 ...	A	B	C	S			
SLY 2 085 ...	8.1	3	3.6	3.0	SLY 2 139 ...	10.4	3	5.9	3.5			
SLY 2 098 ...	8.5		4.0	3.5	13.9	9.4						
	9.8		5.3									
art. no.	dim. [mm]				art. no.	dim. [mm]						
SLY 3 035 ...	A	B	C	S	SLY 3 082 ... G	A	B	C				
SLY 3 041 ...	1.5	2.8	3.5	3.5	SLY 3 082 ... Z	1.5	2.8	8.2				
			4.1									
art. no.	dim. [mm]				art. no.	dim. [mm]						
SLY 4 035 ...	A	B	C	S	SLY 4 082 ... G	A	B	C				
SLY 4 041... G	1.5	2.8	3.5	3.5	SLY 4 082 ... Z	1.5	2.8	8.2				
SLY 4 041... Z			4.1	—								
please indicate: ... no. of contacts												
one row 1 - 50												
two rows 4 - 100												
... surface of contact												
S = selective gold-plated												
G = gold-plated												
Z = tin-plated												

Male headers




Design, matching for BLY ... → G 88

- are used for interconnections of stacked PCBs
- within the total length of the pin the insulator position can be changed as required ... **Design specification-sheet**
- **separable!** any requested number of contact can be delivered

– one row, □ 0.5 mm

									
art. no.	dim. [mm]								
	A			L			S		
SLY 5 040 ...	4.0			10.4			3.5		
SLY 5 075 ...	7.5			13.9					
SLY 5 081 ... G	8.1			14.5			—		
SLY 5 081 ... Z									
SLY 5 122 ... G	12.2			18.6					
SLY 5 122 ... Z									
please indicate:	... no. of contacts one row 1 - 50			... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated					

– two rows, □ 0.5 mm

	  		
art. no.	dim. [mm]		
	A	L	S
SLY 6 040 ...	4.0	10.4	3.5
SLY 6 075 ...	7.5	13.9	
SLY 6 081 ... G	8.1	14.5	—
SLY 6 081 ... Z			
SLY 6 122 ... G	12.2	18.6	
SLY 6 122 ... Z			
please indicate:	... no. of contacts two rows 2 - 100	... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated	

Design specification for connectors, grid spacing 2 mm

date: _____

pieces per order: _____

company: _____

name, dept.: _____

town: _____

street: _____

fax: _____

signature: _____


- ☐ inquiry
- ☐ order

surface finish

- ☐ selective gold-plated
- ☐ gold-plated
- ☐ tin-plated

- ☐ one row 1 - 50 contacts possible
- ☐ two rows 2 - 100 contacts possible

number of contacts



dimensions:

L

A

B





C

L = total contact length
A = distance between PCBs
B = solder side
C = insertion side

Male headers


Turned precision male contacts

- suitable for **BLY 10 SHK 14 02 G** → G 89
- signal and high-power contacts
- contacts gold-plated
- other number of contacts / contact surface upon request

		
art. no. SLY 13 SHK 14 02 G	signal contacts 12	high-power contacts 2
surface of contact:	gold-plated	
		
art. no. SLY 14 SHK 14 02 G	signal contacts 12	high-power contacts 2
surface of contact:	gold-plated	

Male headers

□ 0.5 mm



art. no.	dim. [mm]			
	A	B	C	S
SLY 7 SMD 036 ...	5.6	6.3	3.6	3.0
SLY 7 SMD 045 ...	6.5	4.6	4.5	3.5
SLY 7 SMD 062 ...	8.2		6.2	


please indicate:	... no. of contacts one row 4 - 20	... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated	... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (650pcs/reel)
------------------	---------------------------------------	--	---

... packing (option) - additions:

SLY 7 SMD 036-045 ... B TR: 4-15 contacts


Option, for automatic assembly

– reel diameter Ø 330 mm




... SM

... B SM




SLY 7 SMD ... SM




SLY 7 SMD ... B SM



... B TR



SLY 7 SMD 036-045 ... B TR



Male headers

□ 0.5 mm

art. no.	dim. [mm]			
	A	B	C	S
SLY 8 SMD 036 ...	5.6	8.5	3.6	3.0
SLY 8 SMD 045 ...	6.5	6.5	4.5	3.5
SLY 8 SMD 062 ...	8.2		6.2	
please indicate:	... no. of contacts two rows 4 - 40 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated ... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (650pcs/reel)			

... packing (option) - additions:
SLY 8 SMD ... SM; ... B SM: 6-40 contacts
SLY 8 SMD 036-045 ... B TR: 6-30 contacts


Option, for automatic assembly

– reel diameter Ø 330 mm


... SM	
... B SM	
... B TR	

Male headers

□ 0.5 mm


				
art. no.	dim. [mm]			
	A	B	C	S
SLY 9 SMD 040 ...	8.8	3.3	4.0	3.5
SLY 9 SMD 055 ...	10.3		5.5	
please indicate:	... no. of contacts one row 2 - 20	... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated	... packing (optional) B SM = pick and place pad and bar magazine	

Option, for automatic assembly

	
... B SM	  SLY 9 SMD ... B SM

Male headers

□ 0.5 mm

				
art. no.	dim. [mm]			
	A	B	C	S
SLY 10 SMD 040 ...	12.3	6.8	4	3.5
please indicate:	... no. of contacts two rows 4 - 40			
	... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated		... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (700pcs/reel)	

Option, for automatic assembly

– reel diameter Ø 330 mm


	SLY 10 SMD ... B SM
... B SM	
	SLY 10 SMD 040 ... 4-16 ... B TR SLY 10 SMD 040 ... 18-40 ... B TR
... B TR	

Male headers


Design, matching for BLY ... → G 88

- are used to connect overlying PCBs
- within the total length of the pin the insulating body is variable upon request
- **separable!** every requested number of contact can be delivered

– one row, □ 0.5 mm

 					
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A		A
SLY 11 SMD 051 ...	5.1	SLY 11 SMD 092 ...	9.2	SLY 11 SMD 133 ...	13.3
please indicate: ... no. of contacts one row 4 - 20 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated					



– two rows, □ 0.5 mm

 					
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A		A
SLY 12 SMD 051 ...	5.1	SLY 12 SMD 092 ...	9.2	SLY 12 SMD 133 ...	13.3
please indicate: ... no. of contacts two rows 4 - 40 ... surface of contact S = selective gold-plated G = gold-plated Z = tin-plated					

Male headers

Pin cross section □ 0.3 mm, straight, slim insulating body



- suitable for female header **BLM ...** → G 94
- une rangée 1-20 pôles
- one row 1-20 contacts



art. no.	dim. [mm]			art. no.	dim. [mm]		
	A	B	C		A	B	C
SLM N 1 063 ...	11.1	3.1	6.3	SLM N 11 063 ...	12.8	4.8	6.3
SLM N 1 092 ...	14.0		9.2	SLM N 11 117 ...	18.2		11.7
SLM N 1 117 ...	16.5		11.7				
please indicate:	... no. of contacts one row 1 - 20			... surface of contact G = gold-plated Z = tin-plated			

Pin cross section □ 0.4 mm, straight, slim insulating body

- matching for female header **BLM ...** → G 94
- one row 1-20 contacts






art. no.	dim. [mm]			art. no.	dim. [mm]		
	A	B	C		A	B	C
SLV N 1 055 ...	9.7	2.5	5.5	SLV N 11 055 ...	12.2	5.0	5.5
SLV N 1 080 ...	12.2		8.0	SLV N 11 080 ...	14.7		8.0
SLV N 1 105 ...	14.7		10.5	SLV N 11 105 ...	17.2		10.5
SLV N 1 130 ...	17.2		13.0				
please indicate:	... no. of contacts one row 1 - 20		... surface of contact G = gold-plated Z = tin-plated				




Male headers

Pin cross section □ 0.4 mm, straight

- suitable for female header **BLM ...** → G 94
- one row 1-36 contacts

									
art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SLV W 1 055 ...	9.7	2.5	5.5	SLV W 11 055 ...	12.2	5.0	5.5		
SLV W 1 080 ...	12.2		8.0	SLV W 11 080 ...	14.7		8.0		
SLV W 1 105 ...	14.7		10.5	SLV W 11 105 ...	17.2		10.5		
SLV W 1 130 ...	17.2		13.0						
please indicate:									
... no. of contacts		... surface of contact		... no. of contacts		... surface of contact			
one row 1 - 36		G = gold-plated		one row 1 - 36		G = gold-plated			
		Z = tin-plated				Z = tin-plated			


- matching for female header **BLM ...** → G 94
- two rows 4-72 contacts
- grid spacing 1.27 x 2.54 mm

									
art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SLV W 2 055 ...	9.7	2.5	5.5	SLV W 22 055 ...	12.2	5.0	5.5		
SLV W 2 080 ...	12.2		8.0	SLV W 22 080 ...	14.7		8.0		
SLV W 2 105 ...	14.7		10.5	SLV W 22 105 ...	17.2		10.5		
SLV W 2 130 ...	17.2		13.0						
please indicate:									
... no. of contacts		two rows 4 - 72		... surface of contact					
				G = gold-plated					
				Z = tin-plated					

Male headers

Straight, pin cross section □ 0.4 mm

- matching for female header **BLV 2 ...** → G 95
- two rows 4-72 contacts
- grid spacing **1.27 x 1.27 mm**






art. no.	dim. [mm]			art. no.	dim. [mm]		
	A	B	C		A	B	C
SLV W 4 055 ...	9.7	2.5	5.5	SLV W 4 105 ...	14.7	2.5	10.5
SLV W 4 080 ...	12.2		8.0	SLV W 4 130 ...	17.2		13.0

please indicate: ... no. of contacts two rows 4 - 72 ... surface of contact G = gold-plated Z = tin-plated




Male headers

Pin cross section matching for BLM ... → G 94,
□ 0.4 mm, 90° angled, expanded insulating body

– one row 1-36 contacts

			
art. no.	dim. [mm] C	art. no.	dim. [mm] C
SLV W 1 KA 030 ...	3.0	SLV W 1 KA 080 ...	8.0
SLV W 1 KA 055 ...	5.5	SLV W 1 KA 105 ...	10.5
please indicate: ... no. of contacts one row 1 - 36 ... surface of contact G = gold-plated Z = tin-plated			




- two rows 6-72 contacts
- grid spacing 1.27 x 2.54 mm
- **packing in a bar magazine**
- **VPE** = packing unit (pieces/tube)
- preferred number of contacts, others upon request

									
art. no.	no. of contacts	packing unit	dim. [mm] C	art. no.	no. of contacts	packing unit	dim. [mm] C		
SLV W 2 KA 030 10 ...	10	78	3.0	SLV W 2 KA 054 10 ...	10	78	5.4		
SLV W 2 KA 030 14 ...	14	55		SLV W 2 KA 054 14 ...	14	55			
SLV W 2 KA 030 16 ...	16	50		SLV W 2 KA 054 16 ...	16	50			
SLV W 2 KA 030 20 ...	20	40		SLV W 2 KA 054 20 ...	20	40			
SLV W 2 KA 030 26 ...	26	31		SLV W 2 KA 054 26 ...	26	31			
SLV W 2 KA 030 30 ...	30	27		SLV W 2 KA 054 30 ...	30	27			
SLV W 2 KA 030 34 ...	34	24		SLV W 2 KA 054 34 ...	34	24			
SLV W 2 KA 030 40 ...	40	20		SLV W 2 KA 054 40 ...	40	20			
SLV W 2 KA 030 50 ...	50	16		SLV W 2 KA 054 50 ...	50	16			
SLV W 2 KA 030 72 ...	72	11		SLV W 2 KA 054 72 ...	72	11			
please indicate: ... surface of contact G = gold-plated Z = tin-plated									

Male headers

Angled, pin cross section □ 0,4 mm

- matching for female header **BLV 2 ...** → G 95
- two rows 4-72 contacts
- **grid spacing 1.27 x 1.27 mm**
- preferred number of contacts, others upon request



art. no.	no. of contacts	dim. [mm] C	art. no.	no. of contacts	dim. [mm] C
SLV W 4 KA 036 10 ...	10	3.6	SLV W 4 KA 060 10 ...	10	6.0
SLV W 4 KA 036 14 ...	14		SLV W 4 KA 060 14 ...	14	
SLV W 4 KA 036 16 ...	16		SLV W 4 KA 060 16 ...	16	
SLV W 4 KA 036 20 ...	20		SLV W 4 KA 060 20 ...	20	
SLV W 4 KA 036 26 ...	26		SLV W 4 KA 060 26 ...	26	
SLV W 4 KA 036 30 ...	30		SLV W 4 KA 060 30 ...	30	
SLV W 4 KA 036 34 ...	34		SLV W 4 KA 060 34 ...	34	
SLV W 4 KA 036 40 ...	40		SLV W 4 KA 060 40 ...	40	
SLV W 4 KA 036 50 ...	50		SLV W 4 KA 060 50 ...	50	
SLV W 4 KA 036 72 ...	72		SLV W 4 KA 060 72 ...	72	

please indicate: ... surface of contact



G = gold-plated

Z = tin-plated






Male headers

Pin cross section $\square 0.4$ mm, expanded insulating body




- suitable for female header **BLM ...** → G 94
- one row 4-20 contacts

							
art. no.	dim. [mm]			art. no.	dim. [mm]		
	A	B	C		A	B	C
SLV W 1 SMD 048 ...	8.2	4	4.8	SLV W 1 SMD 073 ...	10.7	4	7.3
please indicate:	... no. of contacts			... surface of contact			
	one row 4 - 20			G = gold-plated			
				Z = tin-plated			

- suitable for female header **BLM ...** → G 94
- two rows 4-40 contacts
- grid spacing 1.27 x 2.54 mm

												
art. no.	dim. [mm]			art. no.	dim. [mm]							
	A	B	C		A	B	C					
SLV W 2 SMD 048 ...	8.2	6.6	4.8	SLV W 2 SMD 073 ...	10.7	6.6	7.3					
please indicate:												
... no. of contacts		... surface of contact										
two rows 4 - 40		G = gold-plated										
		Z = tin-plated										




- matching for female header **BLV 2 ...** → G 95
- two rows 4-40 contacts
- grid spacing 1.27 x 1.27 mm

									
art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SLV W 4 SMD 048 ...	8.2	5.3	4.8	SLV W 4 SMD 073 ...	10.7	5.3	7.3		
please indicate:	... no. of contacts			... surface of contact					
	two rows 4 - 40			G = gold-plated					
				Z = tin-plated					

Male headers

Pin cross section □ 0.4 mm, expanded insulating body



- matching for female header **BLM ...** → G 94
- one row 2-20 contacts

									
art. no.	dim. [mm]			art. no.	dim. [mm]				
	A	B	C		A	B	C		
SLV W 3 SMD 048 ...	9.5	3	4.8	SLV W 3 SMD 073 ...	12.0	3	7.3		
please indicate:	... no. of contacts one row 2 - 20			... surface of contact G = gold-plated Z = tin-plated			... packing (optional) SM = bar magazine		

... packing (option) - additions:

SLV W 3 SMD ... SM: 4-20 contacts

Option, for automatic assembly

					
... SM		SLV W 3 SMD 048 ... SM		SLV W 3 SMD 073 ... SM	

Male headers

Precision contacts, solder and plug pins, Ø 0.43 mm

- turned precision contacts, less space required on PCB
- other number of contacts on request

art. no.	no. of contacts	art. no.	no. of contacts
SLR 1 025 ...	25	SLR 1 050 ...	50
please indicate: ... surface of contact G = gold-plated Z = tin-plated			
art. no.	no. of contacts	art. no.	no. of contacts
SLR 2 050 G	50		
art. no.	no. of contacts	art. no.	no. of contacts
SLR 3 025 G	25	SLR 3 050 G	50
art. no.	no. of contacts	art. no.	no. of contacts
SLR 4 050 G	50	SLR 4 100 G	100
surface of contact: gold-plated			

Male headers

Precision contacts, solder and plug pins Ø 0.43 mm

- less space required on PCB
- other number of contacts on request

art. no.	no. of contacts		no. of contacts
SLR 5 SMD 50 G	50		50
surface of contact:	gold-plated		


Customer specified male and female headers

We manufacture male and female headers for your specific application.

All pin lengths from 7.5 to 45.3 mm for grid 2.54 mm and 7.5 to 30 mm for grid 2.00 mm available on request.

The insulator can be mounted at any requested position on the full length of the pin.


Grid spacing insertion with selective gold-plated contacts on request.




PCB connector,
extra long and additionally stabilized




4-contact male header for THR-soldering;
grid 5.75 mm



8-contact male header with special
insulating body including locating pin




angled male header with two insulators



male header in 5.08 mm grid and
customised




angled male and female header
1.27 mm grid, with customised
insulators



insulator body and precision contacts
according to customer's request











male header with various pin lengths





female header in 5.08 mm grid

Female headers




Precision contacts for pin cross section Ø 0.5 mm

art. no.			art. no.		
MK 01 ...			MK 201 ...		
art. no.			art. no.		
MK 17 ...			MK 217 ...		
art. no.			art. no.		
MK 31 ...			MK 231 ...		
art. no.			art. no.		
MK 12 X 2 ...			MK 212 X 2 ...		
please indicate: ... no. of contacts ... surface of contact one row 1 - 50 G = gold-plated two rows 2 - 100 Z = tin-plated					

			
art. no.	dim. [mm] X	art. no.	dim. [mm] X
MK 13 X 1 ...	5.9	MK 213 X 1 ...	5.9
MK 13 X 2 ...	8.9	MK 213 X 2 ...	8.9
please indicate: ... no. of contacts ... surface of contact one row 1 - 50 G = gold-plated two rows 2 - 100 Z = tin-plated			
contact spring:		gold-plated	



Female headers

Precision contacts for pin cross section Ø 0.5 mm


art. no.			
MK 06 ...			
art. no.			art. no.
MK 07 ...			
			
please indicate:			
... no. of contacts		... surface of contact	
one row 1 - 50		G = gold-plated	
two rows 2 - 100		Z = tin-plated	

Low profile, less than 2.7/3.1 mm - with contact spring for pin cross section Ø 0.5 mm

– solder pin Ø 0.76 mm

art. no.		art. no.	
MK LP 18 ...			
MK LP 19 ...			
please indicate:			
... no. of contacts		... surface of contact	
one row 1 - 50		G = gold-plated	
two rows 4 - 100		Z = tin-plated	
contact spring:		gold-plated	



Low profile: 2.7/3.1 mm; standard profile: 4 mm



Female headers

Precision contacts in THR-soldering technology for pin cross section Ø 0.5 mm


– THR: Through-Hole-Reflow-soldering technology (connector to be soldered with modified insert technique in Reflow-soldering method)



art. no.		
MK 228 THR ...		
please indicate:	... no. of contacts two rows 2 - 40	... surface of contact G = gold-plated Z = tin-plated
contact spring:	gold-plated	

Female headers

Peel-Off



- precision contacts are mounted in a temperature-resistant carrier strip which is removed after soldering
- special loadings upon request

art. no.		
PO A ... G		
please indicate: ... no. of contacts from 2 pins to endless		
contact sleeve:	gold-plated	
contact spring:	gold-plated	
annotation:	Technical data of carrier foil: max. tensile strength: 193 N/mm ² max. thermal expansion - longitudinal direction: 1.7x10 ⁻⁵ mm/°C melting point: 250°C	

Female headers

Precision contacts on metal strip for pin cross section Ø 0.5 mm





art. no.			
SIL 1 ...			
art. no.			
SIL 2 ...			
art. no.			
SIL 3 ...			
please indicate: ... no. of contacts one row 2 - 100 ... surface of contact G = gold-plated Z = tin-plated			
contact spring:		gold-plated	
annotation:		carrier strip: brass	

Female headers

Stamped contact spring (fork contact)







– **separable!** any requested number of contact can be delivered

– for □ 0.635 mm pin cross section, straight

art. no.			
BL 1 ...			
art. no.			
BL 2 ...			
please indicate:			
... no. of contacts		... surface of contact	
one row 1 - 36		G = gold-plated	
two rows 2 - 72		Z = tin-plated	

– for □ 0.635 mm pin cross section, angled

– **BL 4 ...:** packing (option) bar magazine (≥ 6 contacts)

art. no.					
BL 3 ...					
art. no.					
BL 4 ...					
please indicate:					
... no. of contacts		... surface of contact			
one row 1 - 36		G = gold-plated			
two rows 2 - 72		Z = tin-plated			

Female headers

Low profile, fork contact spring

– **separable!** any requested number of contact can be delivered

– for $\square$ 0.635 mm pin cross section, straight


art. no.				
BL LP 1 ...				
art. no.				
BL LP 2 ...				
please indicate: ... no. of contacts one row 1 - 36 two rows 2 - 72 ... surface of contact S = selective gold-plated Z = tin-plated				

– for $\square$ 0.635 mm pin cross section, angled

– **BL LP 4 ...:** packing in a bar magazine (min. 4 contacts)

art. no.				
BL LP 3 ...				
art. no.				
BL LP 4 ...				
please indicate: ... no. of contacts one row 1 - 36 two rows 2 - 72 ... surface of contact S = selective gold-plated Z = tin-plated				

Female headers



For □ 0.635 mm pin cross section, can be put through / 260 °C Reflow

- for each contact both contact springs have to be interconnected via the PCB
- **packing:** bar magazine
- stamped contact spring; - **separable!** any requested number of contact can be delivered

art. no.	dim. [mm] A	art. no.	dim. [mm] A
BL 11 254 ...	2.54	BL 11 508 ...	5.08
please indicate: ... no. of contacts one row 1 - 45 ... surface of contact S = selective gold-plated Z = tin-plated			

For □ 0.635 mm pin cross section, can be put through

- **packing:** bar magazine
- stamped contact spring; - **separable!** any requested number of contact can be delivered

art. no.	dim. [mm] A	art. no.	dim. [mm] A
BL 12 650 ...	6.50	BL 12 762 ...	7.62
art. no.	dim. [mm] A	art. no.	dim. [mm] A
BL 21 650 ...	6.50	BL 21 762 ...	7.62
please indicate: ... no. of contacts two rows 2 - 90 ... surface of contact S = selective gold-plated Z = tin-plated			

G 65

Single precision contacts
 Single contacts metal strip
 High-precision female headers THT
 High-prec. male headers 2.54 THT

→ F 17 - 18
 → G 62
 → G 2 - 6
 → G 58 - 68

Jumpers
 Direct female connectors
 Male headers 2.54 SMD
 Technical data

→ G 100 - 101
 → G 99
 → G 23 - 30
 → G 102 - 108

Female headers


Precision contacts for $\square$ 0.635 mm and $\varnothing$ up to 0.85 mm pin cross section

art. no.	inner contact spring surface
BL 5 ...	$\geq 0,75 \mu\text{m Au}$
BL 5 025 ...	$\geq 0,25 \mu\text{m Au}$
please indicate: ... no. of contacts one row 1 - 36	
art. no.	inner contact spring surface
BL 6 ...	$\geq 0,75 \mu\text{m Au}$
BL 6 025 ...	$\geq 0,25 \mu\text{m Au}$
please indicate: ... no. of contacts two rows 2 - 72	
contact sleeve:	tin-plated
contact spring:	gold-plated
art. no.	
BL KG 3 ...	
please indicate: ... no. of contacts three rows 9 - 96	
art. no.	
BL 7 ...	
please indicate: ... no. of contacts one row 1 - 36	
contact sleeve:	tin-plated
contact spring:	gold-plated



Female headers

Precision contacts for □ 0.635 mm and Ø up to 0.85 mm pin cross section

- packing in a bar magazine (≥ 6 contacts)
- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.		
BL 8 ...		
please indicate: ... no. of contacts two rows 4 - 72		
contact sleeve:	tin-plated	
contact spring:	gold-plated	





- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.		
MK 21 ...		
please indicate: ... no. of contacts one row 1 - 50		
art. no.		
MK 221 ...		
please indicate: ... no. of contacts two rows 2 - 100		
contact sleeve:	tin-plated	
contact spring:	gold-plated	





Female headers

Precision contacts for □ 0.635 mm and Ø up to 0.85 mm pin cross section

- with aligned Wire-Wrap pins
- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.			
BL 9 ...			
please indicate: ... no. of contacts one row 1 - 36			
art. no.			
BL 10 ...			
please indicate: ... no. of contacts two rows 2 - 72			
contact sleeve:	tin-plated		
contact spring:	gold-plated		

- for PC 104 modules
- no capillary action when soldering due to protected contact insert
- **separable!** any requested number of contact can be delivered


art. no.			
BL 13 ...			
please indicate: ... no. of contacts one row 1 - 36			
art. no.			
BL 14 ...			
please indicate: ... no. of contacts two rows 2 - 72			
contact sleeve:	gold-plated		
contact spring:	gold-plated		

Female headers


Precision contacts for $\square 0.635$ mm and $\varnothing$ up to 0.85 mm pin cross section

- for PC 104 modules
- no capillary action when soldering due to protected contact insert
- **separable!** any requested number of contact can be delivered

– one row, 1-36 contacts

	
art. no.	dim. [mm] A
BL 18 141 ...	14.1
BL 18 219 ...	21.9
please indicate: ... no. of contacts one row 1 - 36	
contact sleeve:	gold-plated
contact spring:	gold-plated


– two rows, 2-72 contacts

	
art. no.	dim. [mm] A
BL 19 141 ...	14.1
BL 19 219 ...	21.9
please indicate: ... no. of contacts two rows 2 - 72	
contact sleeve:	gold-plated
contact spring:	gold-plated

Female headers

Turned precision female contacts




- suitable for **SL 26 SHK 14 02 G → G 19** and **SL 27 SHK 14 02 SMD G → G 31**
- signal and high-power contacts
- contacts gold-plated
- other number of contacts / contact surface upon request








Female headers

Low profile, fork contact spring

- for □ 0.635 mm pin cross section
- other number of contacts on request

art. no.				
BL LP 5 SMD ...				
please indicate:	... no. of contacts one row 4 - 20	... surface of contact S = selective gold-plated Z = tin-plated	... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine	

Option, for automatic assembly

				
... SM ... B SM	BL LP 5 SMD ... B		BL LP 5 SMD ... SM	BL LP 5 SMD ... B SM

Female headers

art. no.				
BL LP 6 SMD ...				
please indicate:	... no. of contacts two rows 4 - 40	... surface of contact S = selective gold-plated Z = tin-plated	... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine	

... packing (option) - additions:

BL LP 6 SMD ... SM 6-40 contacts

BL LP 6 SMD ... B SM 4-40 contacts

Option, for automatic assembly

... SM	BL LP 6 SMD ... B	BL LP 6 SMD ... SM	BL LP 6 SMD ... B SM
... B SM			

art. no.				
BL LP 7 SMD ...				
please indicate:	... no. of contacts one row 1 - 20	... surface of contact S = selective gold-plated Z = tin-plated	... packing (optional) SM = bar magazine	

... packing (option) - additions:

BL LP 7 SMD ... SM 4-20 contacts


Option, for automatic assembly

... SM	BL LP 7 SMD ... SM

Female headers

Precision contacts for $\square 0.635$ mm and $\varnothing$ up to 0.85 mm pin cross section

- no capillary action when soldering due to protected contact insert
- **separable!** any requested number of contact can be delivered

			
art. no.	dim. [mm]		
	A	B	C
BL 15 SMD 043...	4.3	5.0	2.5
BL 15 SMD 089...	8.9	9.5	4.8
please indicate:	... no. of contacts one row 4 - 20	... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (400pcs/reel)	

... packing (option) - additions:

BL 15 SMD ... B TR: 4-12 contacts

contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly

- reel diameter $\varnothing$ 330 mm

	... SM	BL 15 SMD 043 ... SM	BL 15 SMD 043 ... B SM
	... B SM	BL 15 SMD 089 ... SM	BL 15 SMD 089 ... B SM
	... B TR		

Female headers

Precision contacts for $\square$ 0.635 mm and $\varnothing$ up to 0.85 mm pin cross section

- no capillary action when soldering due to protected contact insert
- **separable!** any requested number of contact can be delivered

art. no.	dim. [mm]
BL 16 SMD 067 ...	A B C
BL 16 SMD 113 ...	A B C
please indicate: ... no. of contacts two rows 4 - 40 ... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel ... positioning (optional) PS = locating pin (2 pcs/bar bigger than 6 contacts)	

... packing (option) - additions:

BL 16 SMD 067 ... B TR: 4-6 contacts, 500 pcs/reel

BL 16 SMD ... B TR: 6-40 contacts, 250 pcs/reel

contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly

- reel diameter $\varnothing$ 330 mm

... SM ... B SM	BL 16 SMD ... SM BL 16 SMD ... B SM
... B TR	BL 16 SMD 067 ... 4-6 B TR BL 16 SMD 067-113 ... 6-24 B TR BL 16 SMD 067-113 ... 26-40 B TR

Female headers 1.27 SMD
Female headers 2.00 SMD
Female headers 2.54 press-fit
Single contacts metal strip

→ G 97
→ G 90
→ G 82
→ G 62

Single precision contacts
Male headers 2.54 THT
Male headers 2.54 SMD
Technical data



→ F 17 - 18
→ G 7 - 18
→ G 23 - 30
→ G 102 - 108

G 74

Female headers

Precision contacts for $\square 0.635$ mm and $\varnothing$ up to 0.85 mm pin cross section

- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.					
BL 17 SMD ...					
please indicate:	... no. of contacts one row 2 - 20		... packing (optional) SM = bar magazine TR = tape and reel (1,300pcs./reel)		

packing (option) - additions:



BL 17 SMD ... SM: 3-20 contacts

BL 17 SMD ...TR: 2-13 contacts

contact sleeve:	tin-plated
contact spring:	gold-plated





Option, for automatic assembly

- reel diameter $\varnothing 330$ mm

	
... SM	BL 17 SMD ... SM
	
... TR	BL 17 SMD ... TR

Female headers

- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered



art. no.					
BL 20 SMD ...		14,7 7 10,1	Ø 0,6	n/2 x 2,54 2,54 5	4,6 2,54 3
please indicate: ... no. of contacts two rows 4 - 40 ... packing (optional) SM = bar magazine TR = tape and reel (600pcs/reel)					

... packing (option) - additions:

BL 20 SMD ... TR: 4-26 contacts



contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly

	
... SM	BL 20 SMD ... SM
	
... TR	BL 20 SMD ... 4-26 TR

Turned precision female contacts

- suitable for **SL 26 SHK 14 02 G** → G 19 and **SL 27 SHK 14 02 SMD G** → G 31
- signal and high-power contacts
- contacts gold-plated
- other number of contacts / contact surface upon request

		
art. no.	signal contacts	high-power contacts
BL 23 SHK 14 02 SMD G	12	2
surface of contact:	gold-plated	

Single contacts metal strip

Male headers 2.54 THT

Male headers 2.54 SMD

High-precision female headers THT

→ G 62

→ G 7 - 18

→ G 23 - 30

→ G 2 - 6

Female headers 1.27 SMD

Female headers 2.00 SMD

Female headers 2.54 press-fit

Technical data

→ G 97

→ G 90

→ G 82

→ G 102 - 108

G 76

A

B

C

D

E

F

G

H

I

K

L

M

N

Female headers

Precision contacts for $\square$ 0.635 mm and $\varnothing$ up to 0.85 mm pin cross section

- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.			
MK 22 SMD ...			
please indicate:	... no. of contacts one row 4 - 20	... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (600pcs/reel)	

... packing (option) - additions:

MK 22 SMD ... B TR: 3-22 contacts

contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly

	... B SM		MK 22 SMD ... B SM	
	... B TR		MK 22 SMD ... 3-13 B TR MK 22 SMD ... 14-22 B TR	

Female headers

art. no.		
MK 222 SMD ...		
please indicate:	... no. of contacts two rows 4 - 40 ... packing (optional) B SM = pick and place pad and bar magazine	
contact sleeve:	tin-plated	
contact spring:	gold-plated	

Option, for automatic assembly

... B SM	

Precision contacts for $\square$ 0.635 mm and up to $\varnothing$ 0.85 mm pin cross section

- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.		
MK 24 SMD ...		
please indicate:	... no. of contacts one row 2 - 20	
contact sleeve:	tin-plated	
contact spring:	gold-plated	

Precision contacts for pin cross section $\varnothing$ 0.5 mm

- one row
- no capillary action when soldering due to protected contact insert
- **separable!** any requested number of contact can be delivered

art. no.		
MK 25 SMD ...		
please indicate:	... no. of contacts one row 2 - 20	
contact sleeve:	tin-plated	
contact spring:	gold-plated	

Female headers

Precision contacts for pin cross section $\varnothing 0.5$ mm

- one row
- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.			
MK 23 SMD ...			
please indicate:	... no. of contacts one row 4 - 20	... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (600pcs/reel)	

... packing (option) - additions:

MK 23 SMD ... B TR: 3-22 contacts


contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly



		MK 23 SMD ... B SM
... B SM		
		MK 23 SMD ... 3-13 B TR
... B TR		MK 23 SMD ... 14-22 B TR

Female headers

- two rows
- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.	 		
MK 223 SMD ...			
please indicate:	... no. of contacts two rows 4 - 40	... packing (optional) B SM = pick and place pad and bar magazine	
contact sleeve:	tin-plated		
contact spring:	gold-plated		





Option, for automatic assembly

			
... B SM			

Female headers

Precision contacts for pin cross section Ø 0.5 mm

- no capillary action when soldering due to protected contact insert
- **separable!** any requested number of contact can be delivered

art. no.					
MK 220 SMD ...					
please indicate:	... no. of contacts two rows 4 - 40	... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel			

... packing (option) - additions:








MK 220 SMD ... BTR 6-12 contacts; 800 pcs/reel

MK 220 SMD ... BTR 14-40 contacts; 500 pcs/reel

contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly

- reel diameter Ø 330 mm

			
... B SM			MK 220 SMD ... B SM
			
... B TR	MK 220 SMD ... 6-12 B TR	MK 220 SMD ... 14-40 B TR	


Female headers

Precision contacts for $\square$ 0.635 mm and up to $\varnothing$ 0.85 mm pin cross section in pressfit technology

- press-fit mounting without soldering, resilient press-fit area
- no capillary action when soldering due to protected inner contact contact
- Pressfit bar with insulating body has to be inserted up to the PCB
- **separable!** any requested number of contact can be delivered

art. no.				
BLP 1 ...				
BLP 2 ...				
please indicate: ... no. of contacts one row 1 - 36 two rows 2 - 72				
contact sleeve:	tin-plated			
contact spring:	gold-plated			

Hole diameter in PCB - hole structure acc. to DIN EN 60352-5



Female headers

Female connectors for LED applications, low profile, fork contact spring

- **separable!** any requested number of contact can be delivered
- insulating body made of white plastic (nature)
- for $\square$ 0.635 mm pin cross section, straight

art. no.				
BL LP 9 LED ...				
please indicate:	... no. of contacts one row 1 - 36	... surface of contact S = selective gold-plated Z = tin-plated		

Female headers

Female connectors for LED applications

- **separable!** any requested number of contact can be delivered
- insulating body made of white plastic (nature)
- for $\square$ 0.635 mm pin cross section, straight

art. no.				
BL LP 8 LED SMD ...				
please indicate:	... no. of contacts one row 1 - 20	... surface of contact S = selective gold-plated Z = tin-plated	... packing (optional) SM = bar magazine	

... packing (option) - additions:

BL LP 8 LED SMD ... SM 4-20 contacts



Option, for automatic assembly

... SM	BL LP 8 LED SMD ... SM

Female headers

PCB connector for LED-inline modules



- for SMD-soldering technology
- suitable for SMD soldering processes
- simple and save connection assembly
- long life-cycle due to advanced contact geometries and surfaces
- **type of packing: tape and reel (TR) 500 pcs. / tape**

	
art. no.	no. of contacts
BL 40 SMD 2 LED TR	2
	
art. no.	no. of contacts
BL 40 SMD 4 LED TR	4
surface of contact:	tin-plated
soldering section:	tin-plated
color plug housing:	white

Female headers

PCB connector for LED-inline modules



- Through-Hole-Reflow (THR) soldering technology
- suitable for SMD soldering processes
- simple and save connection assembly
- long life-cycle due to advanced contact geometries and surfaces
- **type of packing: tape and reel (TR) 500 pcs. / tape**

	
art. no.	no. of contacts
BL 41 THR 2 LED TR	2
	
art. no.	no. of contacts
BL 41 THR 4 LED TR	4
surface of contact:	tin-plated
soldering section:	tin-plated
color plug housing:	white

Female headers

Plug-in connector for power supply of LED inline modules

- cable connection for different types
- for power supply of LED inline modules
- simple and save connection assembly
- long life-cycle due to advanced contact geometries and surfaces
- **type of packing: loose, in a carton**

				
art. no.		no. of contacts		
BL 42 RDK 2 LED		2		
				
art. no.		no. of contacts		
BL 42 RDK 4 LED		4		
surface of contact:		tin-plated		
soldering section:		tin-plated		
color plug housing:		white		
cross section, rigid:		0.14 mm ² ...0.5 mm ²		
cross section, flexible:		0.2 mm ² ...0.5 mm ²		
cross-section:		AWG 24...20		
cross section core and sleeve (with-out plastic bush):		0.25 mm ² ...0.5 mm ²		

Female headers

Precision contacts for $\square$ 0.5 mm and $\varnothing$ up to 0.56 mm, pin cross section


- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.				
BLY 1 ...				
BLY 2 ...				
BLY 3 ...				
BLY 4 ...				
please indicate: ... no. of contacts one row 1 - 50 two rows 2 - 100				
contact sleeve:	fin-plated			
contact spring:	gold-plated			

Female headers




Turned precision female contacts

- suitable for **SLY 13 SHK 14 02 G** → G 42 and **SLY 14 SHK 14 02 G** → G 42
- signal and high-power contacts
- contacts gold-plated
- other number of contacts / contact surface upon request

					
art. no.		signal contacts		high-power contacts	
BLY 10 SHK 14 02 G		12		2	
surface of contact:			gold-plated		

Female headers




Precision contacts for $\square$ 0.5 mm and $\varnothing$ up to 0.56 mm, pin cross section

art. no.	   		
BLY 5 SMD ...			
please indicate:	... no. of contacts one row 4 - 20	... packing (optional) B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (700pcs/reel)	

... packing (option) - additions:
BLY 5 SMD ... B TR: 4-15 contacts




contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly

	 BLY 5 SMD ... B SM
	 BLY 5 SMD ... 4-15 B TR
... B SM	
... B TR	

Female headers

- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.					
BLY 6 SMD ...					
please indicate:	... no. of contacts one row 2 - 20		... packing (optional) TR = tape and reel		

... packing (option) - additions:






BLY 6 SMD ... TR: 2-10 contacts

BLY 6 SMD ... TR: 11-20 contacts

contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly



- reel diameter Ø 330 mm

			BLY 6 SMD ... TR (2-10 contacts) (2.400 pcs/reel)
... TR			
			BLY 6 SMD ... TR (11-20 contacts) (2.200 pcs/reel)
... TR			

Female headers

Precision contacts for □ 0.5 mm and Ø up to 0.56 mm, pin cross section

- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered






art. no.				
BLY 8 SMD ...				
please indicate: ... no. of contacts two rows 4 - 40 ... packing (optional) SM = bar magazine B SM = pick and place pad and bar magazine B TR = pick and place pad and tape and reel (650pcs/reel)				

... packing (option) - additions:
BLY 8 SMD ... B TR: 6-30 contacts

contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly


- reel diameter Ø 330 mm

		
... B SM	BLY 8 SMD ... B SM	BLY 8 SMD ... SM
		
... B TR	BLY 8 SMD ... B TR	

Female headers

Precision contacts for □ 0.5 mm and Ø up to 0.56 mm pin cross section

- no capillary action when soldering due to protected inner contact
- **separable!** any requested number of contact can be delivered

art. no.			
			
BLY 9 SMD ...			
please indicate:	... no. of contacts two rows 4 - 40	... packing (optional) SM = bar magazine TR = tape and reel (800pcs./reel)	

... packing (option) - additions:

BLY 9 SMD ... SM: 8-40 contacts

BLY 9 SMD ... TR: 4-20 contacts

contact sleeve:	tin-plated
contact spring:	gold-plated

Option, for automatic assembly

- reel diameter Ø 330 mm

... SM

BLY 9 SMD ... SM



... TR

BLY 9 SMD ...TR





Female headers

Stamped contact spring (fork contact)

- matching male header **SLM ...** → G 48 and **SLV ...** → G 48
- one row 1-36 contacts




			
art. no.	dim. [mm]	art. no.	dim. [mm]
BLM KG 1 ...	3.0	BLM LG 1 ...	5.1
please indicate: ... no. of contacts one row 1 - 36 ... surface of contact G = gold-plated Z = tin-plated			

- suitable for male header **SLV** → G 48
- two rows 4-72 contacts - grid spacing 1.27 x 2.54 mm

			
art. no.	dim. [mm]	art. no.	dim. [mm]
BLM KG 2 ...	3.0	BLM LG 2 ...	5.1
please indicate: ... no. of contacts two rows 4 - 72 ... surface of contact G = gold-plated Z = tin-plated			

Female headers

- suitable for male header **SLVW 4 ...** → G 50
- two rows 4-72 contacts
- Vorzugspolzahlen, andere auf Anfrage
- verzinnte Kontakte auf Anfrage

					
art. no.	no. of contacts				
BLV 2 10 G	10				
BLV 2 20 G	20				
BLV 2 26 G	26				
BLV 2 30 G	30				
BLV 2 40 G	40				
BLV 2 50 G	50				
BLV 2 72 G	72				
surface of contact:		gold-plated			

Female headers

Precision contacts for Ø 0.35...0.46 mm, pin cross section

- no capillary action when soldering due to protected inner contact
- other number of contacts on request!

art. no.	no. of contacts		no. of contacts		art. no.	no. of contacts		no. of contacts		
BLR 1 025 Z	25		25		BLR 1 050 Z	50		50		
art. no.	no. of contacts		no. of contacts		art. no.	no. of contacts		no. of contacts		
BLR 2 050 Z	50		50		BLR 2 100 Z	100		100		
art. no.	no. of contacts		no. of contacts		art. no.	no. of contacts		no. of contacts		
BLR 3 025 Z	25		25		BLR 3 050 Z	50		50		
art. no.	no. of contacts				no. of contacts					
BLR 4 100 Z	100				100					
contact sleeve:			tin-plated							
contact spring:			gold-plated							

Shroud male head./press-fit mount. → G 33

Female headers 1.27 THT → G 94 – 96

High-prec. male headers 1.27 SMD → G 56

Male headers 1.27 SMD → G 53

Male headers 2.54 press-fit → G 32

Direct female connectors → G 99


High-prec. male head. 1.27 THT → G 55

Technical data → G 102 – 108

Female headers


Fork contact for □ 0.3 mm and □ 0.4 mm pin cross section, wide insulating body

- suitable for male header **SLM ...** → G 48 and **SLV ...** → G 48
- one row 4-20 contacts

art. no.		
BLM 1 SMD ...		
please indicate:	... no. of contacts one row 4 - 20	... surface of contact G = gold-plated Z = tin-plated


Grid spacing 1.27 x 2.54 mm

- suitable for male header **SLV ...** → G 48
- two rows 4-40 contacts

art. no.		
BLM 2 SMD ...		
please indicate:	... no. of contacts two rows 4 - 40	... surface of contact G = gold-plated Z = tin-plated

Fork contact for □ 0.3 mm and □ 0.4 mm pin cross section, wide insulating body



- matching for male header **SLV** → G 48
- one row 2-20 contacts

art. no.		
BLM 3 SMD ...		
please indicate:	... no. of contacts one row 2 - 20	... surface of contact G = gold-plated Z = tin-plated

Female headers

Turned precision contacts for Ø 0.35...0.46 mm


- closed precision turned part with 3-finger contact prevents rising of flux agents
- other number of contacts on request!

		
art. no.	no. of contacts	
BLR 6 SMD 100 Z	100	
		
art. no.	no. of contacts	no. of contacts
BLR 7 SMD 50 Z	50	50
contact sleeve:	tin-plated	
contact spring:	gold-plated	

Direct female connectors

Without short circuit contact for PCB thickness: 0.7...0.9 mm


– for removable connection of digital displays, coding switches, impulse counters




With short circuit contact for PCB thickness: 0.7...0.9 mm

– for removable connection of digital displays, coding switches, impulse counters

– **K*** = arcing contact






For PCB thickness: 1.4...1.8 mm




art. no.	no. of contacts	dim. [mm]		
		A	B	C
DF OB 06	12	21.33	17.70	12.70
DF OB 07	14	23.87	20.24	15.24
DF OB 10	20	31.49	27.86	22.86
DF OB 17	34	49.27	45.64	40.64
surface of contact:		tin-plated		

Jumpers

For 0.6...0.64 mm wire wrap pins and for Ø 0.6...0.7 mm

				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 5 05 G ...	5.08	0.5 µm gold	2	closed, hole for test probe
CAB 5 10 G ...		1.0 µm gold		
CAB 5 Z ...		5.0 µm tin		
				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 4 G ...	2.54	0.1 µm gold	2	closed
				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 6 05 G ...	2.54	0.5 µm gold	2	open, for miniature alligator clip
CAB 6 10 G ...		1.0 µm gold		
CAB 6 Z ...		5.0 µm tin		
please indicate: ... colour S = black R = red B = blue G = grey				

- the flexible contacts are short-circuiting two pins
- the jumpers can be mounted behind and next to each other

				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 9 G ...	2.54	<0.1 µm gold	2	tag, open
please indicate: ... colour S = black R = red				

Male headers 2.54 press-fit
Male headers 2.54 SMD
Male headers 1.27 SMD
Male headers 1.27 THT



→ G 32
→ G 23 – 30
→ G 53
→ G 48 – 51

Female headers 1.27 THT
Design spec., grid 2.54 mm
Female headers 2.54 press-fit
Technical data



→ G 94 – 66
→ G 15
→ G 82
→ G 102 – 108

Jumpers


For □ 0.5 mm and for Ø 0.4...0.5 mm

				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 10 G S	2	0.1 µm Au	2	open, for miniature alligator clip
colour:		black		
				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 11 G S	2	0.1 µm Au	2	open, for miniature alligator clip
colour:		black		

For □ 0.3...0.4 mm and Ø 0.4...0.5 mm

				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 15 G S	1.27	<0.1 µm Au	2	closed, tag
colour:		black		

For □ 0.3...0.4 mm and Ø 0.4...0.5 mm

				
art. no.	grid [mm]	surface of contact	no. of contacts	version
CAB 16 G ...	1.27	<0.1 µm Au	2	closed
please indicate:		... colour S = black R = red B = blue		

	MK ..., MK LP ...	SL 7 - 9	SLU ...	SL KA 3 ..., SL KG 3 ...
contact material	CuZn-alloy		CuSn alloy	CuZn-alloy
surface contact / contact sleeve	Ni+≥0.2μm Au/ Ni+4...6μm Sn		Ni+≥0.2μm Au (se- lective)/ Ni+4...6μm Sn	Ni+≥0.2μm Au/ Ni +4...6μm Sn
shock resistance	50 g			
volume resistance	≤10 mΩ	≤5 mΩ	≤10 mΩ	≤20 mΩ
vibration resistance max.	15 g			
capacity between two adjacent con- tacts	≤0,4 pF			
nominal current	1.5 A	3 A		
nominal voltage	60 V DC	250 V AC	100 V DC	250 V AC
test voltage	1000 V	2000 V	1000 V	
insulating body material	PA 4.6. GF			
temperature range	-40°C... +163°C/ (260°C/10 s)			-40°C... +163°C/ (260°C/5 s)
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ⁷ Ω·m			
	SL ... SHK ...	SL ..., SL ... THR, SLK ..., SL LP ...	SLP 1 ..., SLP 2 ..., SLUP 31 ...	SL ... LED ...
contact material	CuZn-alloy	CuSn alloy		
surface contact / contact sleeve	Ni+≥0.2μm Au	Ni+≥0.2μm Au/ Ni+4...6μm Sn		
volume resistance	≤10 mΩ	≤5 mΩ	≤10 mΩ	≤5 mΩ
nominal current	8.2 A/ 3 A	3 A		
nominal voltage	250 V AC			
test voltage	1000 V	2000 V	1000 V	2000 V
insulating body material	PCT, GF	PA 4.6. GF		LCP
temperature range	-40°C ... +105°C (260°C / 10s)	-40°C... +163°C/ (260°C/10 s)		-40°C...+230°C/ (260°C/10 s)
class of inflammability	UL 94 V-0			
specific insulation resistance		>10 ⁷ Ω·m		>10 ¹⁵ Ω·cm
	SLY ...	SLY ... SHK ...	SLM N ..., SLV N ..., SLV W ...	SLR ...
contact material	CuSn alloy	CuZn-alloy		
surface contact / contact sleeve	Ni+≥0.2μm Au/ Ni +4...6μm Sn	Ni+≥0.2μm Au	Ni+≥0.2μm Au/ Ni+4...6μm Sn	
volume resistance	≤5 mΩ	≤10 mΩ	≤5 mΩ	≤20 mΩ
nominal current	3 A	8.2 A/ 2.5 A	1.5 A	1 A
nominal voltage	100 V DC	250 V AC	125 V AC	100 V AC/ 150 V DC
test voltage	500 V	1000 V	300 V	500 V
insulating body material	PA 4.6. GF	PCT, GF	PA 4.6. GF	PCT, GF
temperature range	-40°C... +163°C/ (260°C/10 s)	-40°C ... +105°C (260°C / 10s)	-40°C... +163°C/ (260°C/10 s)	-40°C... +105°C/ (260°C/10 s)
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ⁷ Ω·m		>10 ⁷ Ω·m	

Technical data: PCB connectors

	MK 06 ..., MK 07/207 ..., MK 12/212 ..., MK 13/213 ..., MK 17/217 ..., MK 31/231 ...	PO A ...	SIL 1 ..., SIL 3 ...	SIL 2 ...
contact material	CuZn-alloy			
surface contact / contact sleeve	Ni+4...6µm Sn	Ni+≥0.2µm Au	Ni+4...6µm Sn	
inner contact spring material	CuBe-alloy			
inner contact spring surface	Ni+0,75µm Au	Ni+0,25µm Au	Ni+0,75µm Au	Ni+0,25µm Au
type internal spring	4-fingers			
plugability for circuit points	□0,22x0,25mm... □0,4x0,55mm/ Ø0,4...0,56mm			
insert depth	2.5...3.6mm	2.5...3.4mm	2.5...3.6mm	
insertion / drawing force	1.8 N/1.4 N			
shock resistance	50 g		50 g	
volume resistance	≤10 mΩ		≤10 mΩ	
vibration resistance max.	15 g		15 g	
capacity between two adjacent con- tacts	≤0,4 pF		≤0,4 pF	
nominal current	1.5 A	3 A	1.5 A	
nominal voltage	60 V DC	150 V DC	60 V DC	
test voltage	1000 V	1000 V / 1 min.	1000 V	
insulating body material	PA 4.6. GF			
temperature range	-40°C... +163°C/ (260°C/10 s)	-55°C... +125°C/ (260°C/10 s)		
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ⁷ Ω·m			

	BL 1 ..., BL 2 ..., BL 3 ..., BL 4 ...	BL LP ...	BL 11 ...	BL 12 ..., BL 21 ...
contact material	CuSn alloy			
surface contact / contact sleeve	Ni+≥0.2μm Au/ Ni +4...6μm Sn	Ni+≥0.2μm Au (se- lective)/ Ni+2...4μm Sn (matt finished tin)	Ni+4...6μm Sn	
type internal spring	fork contact		spring contact	
plugability for circuit points	□0,5...0,7mm		□0,6...0,65mm	
insert depth	1.5...5mm	2...4mm	≥5mm from above/ ≥8mm from below	≥6mm from above or from below
insertion / drawing force	1.5 N/1.3 N	2N/1.5N	1.5 N/0.5 N	1.5 N/0.2 N
volume resistance	≤10 mΩ		≤20 mΩ	
capacity between two adjacent con- tacts	≤ 0,9 pF			
nominal current	3 A			
nominal voltage	125 V AC		250 V AC	
test voltage	1500 V		500 V	
insulating body material	PPS		PA 4.6. GF	LCP
temperature range	-40°C... +200°C/ (260°C/10 s)		-40°C... +163°C/ (260°C/10 s)	-55°C... +125°C
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ¹² Ω·m	>10 ¹² Ω	>10 ⁷ Ω·m	>10 ¹² Ω·m
	BL 5 - 10 ...	BL KG 3 ...	BL 15 - 17 SMD ..., BL 20 SMD ..., BL 5 - 10 ...	BL 13 ..., BL 14 ..., BL 18 ..., BL 19 ...
contact material	CuZn-alloy			
surface contact / contact sleeve	Ni+4...6μm Sn			Ni+≥0.2μm Au
inner contact spring material	CuBe-alloy			
inner contact spring surface		Ni+0,75μm Au		
type internal spring	6-fingers			
plugability for circuit points	□0,55...0,65mm/ Ø0,65...0,85mm			
insert depth	2.5...6mm			
insertion / drawing force	1.3N/0.3N			
shock resistance	50 g		50 g	
volume resistance	≤10 mΩ		≤10 mΩ	
vibration resistance max.	15 g		15 g	
capacity between two adjacent con- tacts	≤ 0,3 pF		≤ 0,3 pF	
nominal current	3 A			
nominal voltage	150 V DC			
test voltage	1500 V	500 V	1500 V	
insulating body material	PA 4.6. GF	PCT, GF	PA 4.6. GF	
temperature range	-40°C... +163°C/ (260°C/10 s)	-55°C... +125°C/ (260°C/10 s)	-40°C... +163°C/ (260°C/10 s)	
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ⁷ Ω·m		>10 ⁷ Ω·m	

Technical data: PCB connectors

	BL ... SHK ...	MK 21/221 ..., MK 22/222 ..., MK 24 SMD ...	MK 01/201 ..., MK 220 SMD ..., MK 228 THR ..., MK 23/223 ..., MK 25 SMD ..., MK LP 18 ..., MK LP 19 ..., MK LP 218 ..., MK LP 219 ...	BLP 1 ..., BLP 2 ...
contact material	CuZn-alloy			
surface contact / contact sleeve	Ni+≥0.2μm Au	Ni+4...6μm Sn		
inner contact spring material		CuBe-alloy		
inner contact spring surface		Ni+0,75μm Au	Ni+0,25μm Au	Ni+0,75μm Au
type internal spring	fork contact	6-fingers	4-fingers	6-fingers
plugability for circuit points	□0,64mm/ □1,14mm	□0,55...0,65mm/ Ø0,65...0,85mm	□0,22x0,25mm... □0,4x0,55mm/ Ø0,4...0,56mm	□0,55...0,65mm/ Ø0,65...0,85mm
insert depth	3.3...5.7mm	2.5...3.6mm		2.5...6mm
insertion / drawing force		1.3N/0.3N	1.8 N/1.4 N	1.3N/0.3N
shock resistance		50 g		
volume resistance		≤10 mΩ		
vibration resistance max.		15 g		
capacity between two adjacent con- tacts		≤0,3 pF	≤0,4 pF	≤ 0,3 pF
nominal current	8.2 A/ 3 A	3 A	1.5 A	2 A
nominal voltage	250 V AC	150 V DC	60 V DC	150 V DC
test voltage	1000 V	1500 V	1000 V	
insulating body material	PCT, GF	PA 4.6. GF		
temperature range	-40°C ... +105°C (260°C / 10s)	-40°C... +163°C/ (260°C/10 s)		
class of inflammability	UL 94 V-0			
specific insulation resistance		>10 ⁷ Ω·m		

	BL LP ... LED ...	BL 40 SMD... LED TR, BL 41 THR ... LED TR, BL 42 RDK ... LED, SL 40 SMD ... LED TR, SL 41 THR ... LED TR	BLY ...	BLY ... SHK ...
contact material	CuSn alloy	Cu-alloy	CuZn-alloy	
surface contact / contact sleeve	Ni+≥0.2μm Au (se- lective)/ Ni+2...4μm Sn (matt finished tin)		Ni+4...6μm Sn	Ni+≥0.2μm Au
surface contact area		Sn 4-8 μm		
surface soldering area		Ni 1,3-3 μm/ Ni 3-5 μm		
surface solder housing		Ni 1,3-3 μm/ Ni 3-5 μm		
inner contact spring material			CuBe-alloy	
inner contact spring surface			Ni+0,25μm Au	
type internal spring	fork contact		6-fingers	fork contact
plugability for circuit points	□0,5...0,7mm	□0,6	□0,45...0,5mm/ Ø0,4...0,56mm	□0,45...0,5mm/ □1,14mm
insert depth	2...4mm	4,5mm	2.5...3.8mm	
insertion / drawing force	2N/1.5N	5N/4N	1.3N/0.3N	
shock resistance			50 g	
volume resistance	≤10 mΩ	3 mΩ	≤10 mΩ	
vibration resistance max.			15 g	
capacity between two adjacent con- tacts	≤ 0,9 pF		≤0,7 pF	
nominal current	3 A	6 A	2.5 A	8.2 A/ 2.5 A
nominal voltage	125 V AC	160 V DC	100 V DC	250 V AC
test voltage	1500 V	1000 V	500 V	
insulating body material	LCP	PA, white	PA 4.6. GF	PCT, GF
temperature range	-40°C...+230°C/ (260°C/10 s)	-40°C... +70°C	-40°C... +163°C/ (260°C/10 s)	-40°C ... +105°C (260°C / 10s)
class of inflammability	UL 94 V-0			
specific insulation resistance	>10 ¹⁵ Ω·cm		>10 ⁷ Ω·m	
creeping current resistance			CTI 600	

Technical data: PCB connectors


	BLM ...	BLV 2 ...	BLR ...	DF 2 ...
contact material	CuSn alloy		CuZn-alloy	CuSn alloy
surface contact / contact sleeve	Ni+ $\geq 0.2\mu\text{m}$ Au/ Ni +4... $6\mu\text{m}$ Sn	Ni+ $\geq 0.2\mu\text{m}$ Au	Ni+4... $6\mu\text{m}$ Sn	
inner contact spring material			CuBe-alloy	
inner contact spring surface			Ni+0,25 μm Au	
type internal spring	fork contact		3-fingers	
plugability for circuit points	$\square 0,3...0,4\text{mm}$	$\square 0,4\text{mm}$	$\varnothing 0,35...0,46\text{mm}$	
insert depth	2.5...6mm	2.5...4.2	2.5...3mm	
insertion / drawing force	1.3 N/1.1 N		1.2N/0.6N	
shock resistance			50 g	
volume resistance	$\leq 10\text{ m}\Omega$		$\leq 20\text{ m}\Omega$	
vibration resistance max.			15 g	
capacity between two adjacent contacts	$\leq 0,4\text{ pF}$		$\leq 1,0\text{ pF}$	
nominal current	1.5 A	1 A		2 A
nominal voltage	125 V AC	100 V DC		125 V AC
test voltage	500 V			
insulating body material	PA 4.6. GF	PCT, GF		polycarbonate
temperature range	-40°C... +163°C/ (260°C/10 s)	-40°C... +105°C/ (260°C/10 s)		-40°C... +125°C
class of inflammability	UL 94 V-0			
specific insulation resistance	$> 10^7\text{ }\Omega\cdot\text{m}$			
PCB thickness				0,7...0,9 mm

	DF OB ...	CAB 5 ...	CAB 4 G ...	CAB 6 ...
contact material	CuSn alloy			
surface contact / contact sleeve	Ni+7µm Sn	0.5 µm Au/ 1 µm Au/ 5 µm Sn	0.1 µm Au/ 5 µm Sn	0.5 µm Au/ 1 µm Au/ 5 µm Sn
type internal spring	spring contact			
insert depth		4...5.5mm	4...6.1mm	5mm...plug through
nominal current	3 A		1.5 A	
nominal voltage	125 V AC	250 V AC		
test voltage	800 V			
insulating body material	PA 4.6. GF	PA 66	PBT	PA 66
temperature range	-40°C... +125°C/ (260°C/10 s)	-40°C... +105°C		
class of inflammability	UL 94 V-0			
PCB thickness	1,4...1,8 mm			
mounting	without mounting eye-lets			
	CAB 9 ...	CAB 10 G S	CAB 11 G S	CAB 15 G S
surface contact / contact sleeve	0.1 µm Au			<0.1µm Au
insert depth	4...5.6mm	4mm...plug through	5mm...plug through	2.2...2.4mm
nominal current	3 A	1.5 A		1 A
nominal voltage	500 V AC	150 V DC		100 V AC
insulating body material	PBT			PA 66
temperature range	-40°C... +105°C/ (re-sistance to soldering heat 235°C/30-60s)	-40°C... +105°C		-40°C... +150°C
	CAB 16 G ...			
surface contact / contact sleeve	<0.1µm Au			
insert depth	2.2...2.4mm			
nominal current	1 A			
nominal voltage	100 V AC			
insulating body material	PBT			
temperature range	-40°C... +105°C			



Shroud male headers

- shroud male headers for lockable multipoint connector
- version: 2 rows, 6 contacts up to 50 contacts, grid 2.54 mm; 2.00 mm; 1.27 mm
- straight, angled and for SMD technology
- reflow solderable insulator
- class of flammability acc. to UL 94 V0




Multipoint connector with and without lock

- multipoint connector for ribbon cable
- version: two rows, 6 contacts up to 50 contacts, grid 2.54mm
- version without lock
- with polarisation



Multipoint connector, one and two rows

- multipoint connector for ribbon cable
- two rows with and without pull relief, grid 2.54, 6 contacts up to 50 contacts
- two rows in grid 2.00 mm; 1.27 mm, 20 contacts up to 50 contacts
- polarisation at the two row version
- one row in grid 2.54 mm, 3 contacts up to 25 contacts





PCB connector

- PCB connector for ribbon cable
- one row in grid 2.54 mm, 4 contacts up to 20 contacts
- two rows in grid 2.54 mm, 6 contacts up to 34 contacts
- two rows in DIL design, grid 2.54 mm, 4 contacts up to 40 contacts

Shroud-male header

Straight, two rows, shrouded

- suitable for female multipoint connector **VFL ...** → H 11, **FLMP ...** → H 11, **PV ...** → H 12
- in addition they can be combined with many other ribbon cable connectors in 2.54 mm pitch
- plug-in area available in gold-plated or completely tin-plated!

									
art. no.	no. of contacts	dim. [mm]			art. no.	no. of contacts	dim. [mm]		
		A	B	C			A	B	C
ASLG 06 ...	6	15.3	12.7	5.08	ASLG 20 ...	20	33.1	30.5	22.86
ASLG 08 ...	8	17.8	15.2	7.62	ASLG 26 ...	26	40.7	38.1	30.48
ASLG 10 ...	10	20.4	17.8	10.16	ASLG 34 ...	34	50.9	48.3	40.64
ASLG 12 ...	12	22.9	20.3	12.70	ASLG 40 ...	40	58.5	55.9	48.26
ASLG 14 ...	14	25.4	22.9	15.24	ASLG 50 ...	50	71.2	68.6	60.96
ASLG 16 ...	16	28.0	25.4	17.78					
please indicate: ... surface of contact G = gold-plated Z = tin-plated									

Angled, two rows, shrouded

- suitable for female multipoint connector **VFL ...** → H 11, **FLMP ...** → H 11, **PV ...** → H 12
- in addition they can be combined with many other ribbon cable connectors in 2.54 mm pitch
- plug-in area available in gold-plated or completely tin-plated!

art. no.	no. of contacts	dim. [mm]					
		A	B	C			
ASLA 06 G	6	15.3	12.7	5.08			
ASLA 08 G	8	17.8	15.2	7.62			
ASLA 10 G	10	20.4	17.8	10.16			
ASLA 12 G	12	22.9	20.3	12.70			
ASLA 14 G	14	25.4	22.9	15.24			
ASLA 16 G	16	28.0	25.4	17.78			
ASLA 20 G	20	33.1	30.5	22.86			
ASLA 26 G	26	40.7	38.1	30.48			
ASLA 34 G	34	50.9	48.3	40.64			
ASLA 40 G	40	58.5	55.9	48.26			
ASLA 50 G	50	71.2	68.6	60.96			

Shroud-male header

SMD, two rows, shrouded

- suitable for female multipoint connector **VFL ...** → H 11, **FLMP ...** → H 11, **PV ...** → H 12
- **VPE** = packing unit (pieces/tube)
- plug-in area available in gold-plated or completely tin-plated
- in addition they can be combined with many other ribbon cable connectors in 2.54 mm pitch

art. no.	no. of contacts	packing unit	dim. [mm]		art. no.	no. of contacts	packing unit	dim. [mm]	
ASL 06 SMD ...	6	32	15.3	5.08	ASL 20 SMD ...	20	15	33.1	22.86
ASL 08 SMD ...	8	27	17.8	7.62	ASL 26 SMD ...	26	12	40.7	30.48
ASL 10 SMD ...	10	24	20.4	10.16	ASL 34 SMD ...	34	9	50.9	40.64
ASL 12 SMD ...	12	21	22.9	12.70	ASL 40 SMD ...	40	8	58.5	48.26
ASL 14 SMD ...	14	19	25.4	15.24	ASL 50 SMD ...	50	7	71.2	60.96
ASL 16 SMD ...	16	17	28.0	17.78					

please indicate: ... surface of contact
G = gold-plated
Z = tin-plated

... packing
SM = bar magazine
B SM = pick and place pad and bar magazine
B TR = pick and place pad and tape and reel (300pcs/reel)

... packing (option) - additions:
ASL 26 SMD ... B TR: 26 contacts


Option, for automatic assembly

... B SM		ASL ... SMD ... ASL ... SMD ... B SM							
... TR		ASL 26 SMD ... B TR							

Shroud-male header

Straight, two rows, shrouded




- suitable for female multipoint connector **PVY ...** → H 13
- they are also combinable with many other ribbon cable female multipoint connectors in grid 2.00 mm
- contacts are available in gold-plated, tin-plating upon request!

 				
art. no.	no. of contacts	dim. [mm]		
		A	B	C
ASLGY 10 G	10	17	15.8	8
ASLGY 20 G	20	27	25.8	18
ASLGY 26 G	26	33	31.8	24
ASLGY 40 G	40	47	45.8	38
ASLGY 44 G	44	51	49.8	42
ASLGY 50 G	50	57	55.8	48

Shroud-male header

Straight, two rows, shrouded and with lock


- suitable for female multipoint connector **PVY ...** → H 13
- they are also combinable with many other ribbon cable female multipoint connectors in grid 2.00 mm
- contacts are available in gold-plated, tin-plating upon request!

							
art. no.	no. of contacts	dim. [mm]					
		A		B			
VSLGY 10 G	10	25.7		8			
VSLGY 20 G	20	35.7		18			
VSLGY 26 G	26	41.7		24			
VSLGY 40 G	40	55.7		38			
VSLGY 44 G	44	59.7		42			
VSLGY 50 G	50	65.7		48			

Shroud-male header

SMD, two rows, shrouded

- suitable for female multipoint connector **PVY ...** → H 13
- they are also combinable with many other ribbon cable female multipoint connectors in grid 2.00 mm
- contacts are available in gold-plated, tin-plating upon request!



Shroud-male header

Straight, two rows, shrouded

- suitable for female multipoint connector **PVV ...** → H 14
- they are also combinable with many other ribbon cable female multipoint connectors in grid 1.27 mm
- contacts are available in gold-plated, tin-plating upon request!

	art. no.	no. of contacts	dim. [mm]	
			A	B
	ASLGV 10 G	10	12.65	11.10
	ASLGV 20 G	20	19.00	17.45
	ASLGV 26 G	26	22.80	21.25
	ASLGV 40 G	40	31.70	30.15
			C	
				5.08
				11.43
				15.24
				24.13

Angled, two rows, shrouded


- suitable for female multipoint connector **PVV ...** → H 14
- they are also combinable with many other ribbon cable female multipoint connectors in grid 1.27 mm
- contacts are available in gold-plated, tin-plating upon request!

	art. no.	no. of contacts	dim. [mm]	
			A	B
	ASLAV 10 G	10	12.65	11.10
	ASLAV 20 G	20	19.00	17.45
	ASLAV 26 G	26	22.80	21.25
	ASLAV 40 G	40	31.70	30.15
			C	
				5.08
				11.43
				15.24
				24.13

Shroud-male header

Straight, two rows, shrouded and with lock

- suitable for female multipoint connector **PVV ...** → H 14
- they are also combinable with many other ribbon cable female multipoint connectors in grid 1.27 mm
- contacts are available in gold-plated, tin-plating upon request!




art. no.	no. of contacts	dim. [mm]	
		A	B
VSLGV 10 G	10	20.83	5.08
VSLGV 20 G	20	27.18	11.43
VSLGV 26 G	26	30.89	15.24
VSLGV 40 G	40	39.88	24.13

Shroud-male header


SMD, two rows, shrouded

- suitable for female multipoint connector **PVV ...** → H 14
- they are also combinable with many other ribbon cable female multipoint connectors in grid 1.27 mm
- contacts are available in gold-plated, tin-plating upon request!

			
art. no.	no. of contacts	dim. [mm]	
ASLV 10 SMD G	10	A	B
ASLV 20 SMD G	20	6.35	5.08
ASLV 26 SMD G	26	12.70	11.43
ASLV 40 SMD G	40	16.51	15.24
		25.40	24.13

SMD, two rows, shrouded and with lock



- suitable for female multipoint connector **PVV ...** → H 14
- they are also combinable with many other ribbon cable female multipoint connectors in grid 1.27 mm
- contacts are available in gold-plated, tin-plating upon request!

			
art. no.	no. of contacts	dim. [mm]	
		A	B
VSLV 10 SMD G	10	20.83	5.08
VSLV 20 SMD G	20	27.18	11.43
VSLV 26 SMD G	26	30.89	15.24
VSLV 40 SMD G	40	39.88	24.13

Female connector

One row




– excess length of the ribbon cable to the case at ≥ 1 mm!

 					
art. no.	no. of contacts	dim. [mm]			
		A	B	C	D
FV 03 ...	3	15.24	7.62	5.08	8.89
FV 04 ...	4	17.78	10.16	7.62	11.43
FV 05 ...	5	20.32	12.70	10.16	7.62
FV 06 ...	6	22.86	15.24	5.08	16.51
FV 07 ...	7	25.40	17.78	15.24	19.05
FV 08 ...	8	27.94	20.32	17.78	21.59
FV 10 ...	10	33.02	25.40	22.86	26.67
FV 12 ...	12	38.10	30.48	27.94	31.75
FV 13 ...	13	40.64	33.02	30.48	34.29
FV 14 ...	14	43.18	35.66	33.02	36.83
FV 16 ...	16	48.26	40.64	38.10	41.91
FV 17 ...	17	50.80	43.18	40.64	44.45
FV 18 ...	18	53.34	45.72	43.18	46.99
FV 20 ...	20	58.42	50.80	48.26	52.07
FV 24 ...	24	68.58	60.96	58.42	62.23
FV 25 ...	25	71.12	63.50	60.96	64.77
please indicate: ... surface of contact G = gold-plated Z = tin-plated					
annotation:		IDC-pattern 2.54mm			
cross-section:		AWG 28...30 = 0,09...0,05 mm ²			
insulation diameter:		≤ 1,1 mm			
suitable ribbon cable round conductor flat cable:		AWG 28 = massive or strand			
recommended connector pins:		□ 0,635 mm			



Female connector

Two rows, with polarisation

– lockable female multipoint connector, suitable for shrouded male header **ASL ...**

							
art. no.	no. of contacts	dim. [mm]		art. no.	no. of contacts	dim. [mm]	
		A	B			A	B
VFL 06 ...	6	23.58	9.56	VFL 20 ...	20	41.36	27.34
VFL 08 ...	8	26.12	12.10	VFL 26 ...	26	48.98	34.96
VFL 10 ...	10	28.66	14.64	VFL 34 ...	34	59.14	45.12
VFL 12 ...	12	31.20	17.18	VFL 40 ...	40	66.76	52.74
VFL 14 ...	14	33.74	19.72	VFL 50 ...	50	79.46	65.44
VFL 16 ...	16	36.28	22.26				
please indicate: ... surface of contact G = gold-plated Z = tin-plated							




- suitable for shrouded male header **ASL ...**
- excess length of the ribbon cable to the case at ≥ 1 mm!

							
art. no.	no. of contacts	dim. [mm]		art. no.	no. of contacts	dim. [mm]	
		A	B			A	B
FLMP 06 ...	6	10.97	9.56	FLMP 20 ...	20	28.75	27.34
FLMP 08 ...	8	13.51	12.10	FLMP 26 ...	26	36.37	34.96
FLMP 10 ...	10	16.05	14.64	FLMP 34 ...	34	46.53	45.12
FLMP 12 ...	12	18.59	17.18	FLMP 40 ...	40	54.15	52.74
FLMP 14 ...	14	21.13	19.72	FLMP 50 ...	50	66.85	65.44
FLMP 16 ...	16	23.67	22.26				
please indicate: ... surface of contact G = gold-plated Z = tin-plated							
annotation:		IDC-pattern 1.27mm					
cross-section:		AWG 28...30 = 0,09...0,05 mm ²					
insulation diameter:		$\leq 1,1$ mm					
suitable ribbon cable round conductor flat cable:		AWG 28 = massive or strand					

Female connector

Two rows, with polarisation

- suitable for shrouded male header **ASL ...**
- excess length of the ribbon cable to the case at ≥ 1 mm!




									
art. no.	no. of contacts	suitable strain relief	dim. [mm] A B		art. no.	no. of contacts	suitable strain relief	dim. [mm] A B	
PV 06 G	6	ZEPV 06	12.2	5.08	PV 26 G	26	ZEPV 26	37.6	30.48
PV 10 G	10	ZEPV 10	17.3	10.16	PV 34 G	34	ZEPV 34	47.8	40.64
PV 14 G	14	ZEPV 14	22.4	15.24	PV 40 G	40	ZEPV 40	55.4	48.26
PV 16 G	16	ZEPV 16	24.9	17.78	PV 50 G	50	ZEPV 50	68.1	60.96
PV 20 G	20	ZEPV 20	30.0	22.86					
surface of contact:			gold-plated						
annotation:			IDC-pattern 1.27mm						
cross-section:			AWG 28...30 = 0,09...0,05 mm ²						
insulation diameter:			≤1,1 mm						
suitable ribbon cable round conductor flat cable:			AWG 28 = massive or strand						

art. no.	no. of contacts	dim. [mm]		art. no.	no. of contacts	dim. [mm]	
ZEPV 06	6	A	B	ZEPV 26	26	A	B
ZEPV 10	10	12.2	5.08	ZEPV 34	34	37.6	30.48
ZEPV 14	14	17.3	10.16	ZEPV 40	40	47.8	40.64
ZEPV 16	16	22.4	15.24	ZEPV 50	50	55.4	48.26
ZEPV 20	20	24.9	17.78			68.1	60.96
		30.0	22.86				

Female connector

Two rows




- Suitable for **ASLGY ...**, **ASLY ... SMD** and **VSLGY ...**
- Protrusion length of the ribbon cable to the case ≥ 1 mm!

									
art. no.	no. of contacts	dim. [mm]							
		A			B				
PVY 10 S	10	15.2			8				
PVY 20 S	20	25.1			18				
PVY 26 S	26	31.2			24				
PVY 40 S	40	45.3			38				
PVY 44 S	44	49.3			42				
PVY 50 S	50	55.1			48				
surface of contact:		selective gold-plated							
annotation:		IDC-pattern, 1 mm							
recommended connector pins:		□ 0,5 mm							

Female connector

Two rows

- Suitable for **ASLGV ...**, **ASLAV ...**, **VSLGV ...**, **ASLV ... SMD** und **VSLV ... SMD**
- Protrusion length of the ribbon cable to the case ≥ 1 mm!

					
art. no.	no. of contacts	dim. [mm]			
		A	B		
PVV 10 G	10	10.54	5.08		
PVV 20 G	20	16.89	11.43		
PVV 26 G	26	20.70	15.24		
PVV 40 G	40	29.59	24.13		
surface of contact:		gold-plated			
annotation:		IDC-pattern 0.635mm			
recommended connector pins:		□ 0,4 mm			

Printed circuit connector

– excess length of the ribbon cable to the case at ≥ 1 mm!

	3 3,2 0,35 1,27 A B 2,54 C 0,45 7,2			
art. no.	no. of contacts	dim. [mm]		
		A	B	C
SBAU 1 04 Z	4	17.78	10.16	7.62
SBAU 1 06 Z	6	22.86	15.24	12.70
SBAU 1 08 Z	8	27.94	20.32	17.78
SBAU 1 10 Z	10	33.02	25.40	22.86
SBAU 1 12 Z	12	38.10	30.48	27.94
SBAU 1 14 Z	14	43.18	35.56	33.02
SBAU 1 16 Z	16	48.26	40.64	38.10
SBAU 1 17 Z	17	50.80	43.18	40.64
SBAU 1 18 Z	18	53.34	45.72	43.18
SBAU 1 20 Z	20	58.42	50.80	48.26
surface of contact:		tin-plated		
annotation:		IDC-pattern 2.54mm		
insulation diameter:		≤1,1 mm		
suitable ribbon cable round conductor flat cable:		AWG 28 = massive or strand		


– excess length of the ribbon cable to the case at ≥ 1 mm!

art. no.	no. of contacts	dim. [mm]		
		A	B	C
SBAU 06 Z	6	12.9	7.8	5.08
SBAU 10 Z	10	18.0	12.9	10.16
SBAU 14 Z	14	23.0	18.0	15.24
SBAU 16 Z	16	25.6	20.5	17.78
SBAU 20 Z	20	30.7	25.6	22.86
SBAU 26 Z	26	38.3	33.2	30.48
SBAU 34 Z	34	48.5	43.4	40.64
surface of contact:		tin-plated		
annotation:		IDC-pattern 1.27mm		
insulation diameter:		≤1,1 mm		
suitable ribbon cable round conductor flat cable:		AWG 28 = massive or strand		

Printed circuit connector



Design DIL

– excess length of the ribbon cable to the case at ≥ 1 mm!

							
art. no.	no. of contacts	dim. [mm]					
		A	B	C	D	E	
KK 04 Z	4	8.0	5.1	2.54	7.62	11.0	
KK 06 Z	6	10.3	7.6	5.08			
KK 08 Z	8	13.0	10.2	7.62			
KK 10 Z	10	15.4	12.7	10.16			
KK 12 Z	12	18.0	15.3	5.08			
KK 14 Z	14	20.5	17.8	15.24			
KK 16 Z	16	23.0	20.3	17.78			
KK 18 Z	18	25.6	22.9	20.32			
KK 20 Z	20	28.1	25.4	22.86	15.24	18.7	
KK 24 Z	24	33.0	30.5	27.94			
KK 28 Z	28	38.1	35.6	33.02			
KK 40 Z	40	53.3	50.8	48.26			
surface of contact:		tin-plated					
annotation:		IDC-pattern 1.27mm					
insulation diameter:		≤1,1 mm					
suitable ribbon cable round conductor flat cable:		AWG 28 = massive or strand					

Accessories for flat ribbon cable and application tools

Flat ribbon cable - Spacing 2.54 mm - suitable for connectors FV, SBAU 1

	
art. no.	no. of contacts
BK 01 32	32

Bench press

- height without handle: 28 cm, weight: 9.02 kg
- the bench press **VBK 1** connects all contacts of IDC connector types **FLMP, FV, KK, PV, PVY, SB, VFL, DS/DB BK 09-37** in one simple operation
- the contacts separate the insulation of the flat ribbon cable, whereas a gas-tight and corrosion-proof connection is effected by the construction of the contacts form

	
art. no.	
VBK 1	

Accessories, suitable for ribbon cable connector

- exchangeable crimping dies for any indicated types available

art. no.	suitable for male connectors and female headers
KK W	KK
PV W	FLMP/ PV/ VFL
PVY W	PVY
SB W	SB
D W 9 37	D-Sub (9-37 contacts)

	ASL ..., ASLG ...	ASLGY ..., ASLY ... SMD G, VSLGY ...	ASLAV ..., ASLGV ..., ASLV ... SMD G, VSLGV ..., VSLV ... SMD G	FV ...
surface contact / contact sleeve	Ni+≥0.2μm Au/ Ni +4...8μm Sn	Ni+≥0.2μm Au		Ni+≥0.2μm Au/ Ni +5...10μm Sn
contact material	CuSn alloy	Cu-alloy		CuSn alloy
creeping current resistance				KC 175 nach DIN 53480
creepage	≥1,1mm VDE0110			1,4mm VDE0110
air gap	≥0,8 mm VDE0110			1mm VDE0110
nominal current	1 A	1.5 A	1 A	2 A
nominal voltage	250V AC insulation group A, according to VDE0110	150 V DC	100 V DC	250V AC insulation group A, according to VDE0110
test voltage	500 V AC		300 V AC	500 V AC
insertion / drawing force				≥0.3N ... ≤0.7N per contact
cycles of operation				≥50 according to DIN 41640
insulating body material	PPS	PBT		PC/ colour: RAL 7032
temperature range	-40°C ... +200°C (260°C / 10s)	-40°C ... +105°C (260°C / 10s)		-55°C... +125°C
class of inflammability	UL 94 V-0			
specific insulation resistance	> 10 ⁷ Ω·m			
cross-section				AWG 28...30 = 0,09...0,05 mm ²
	FLMP ..., VFL ...	PV ...	PVY ... S	PVW ... G
surface contact / contact sleeve	Ni+≥0.2μm Au/ Ni +5...10μm Sn	Ni+≥5μm Sn/ Ni +≥0.2μm Au	contact area: Ni + >0.1μm Au/ con- nection area: Ni +0.5...2.5μm Sn	contact area: Ni + >0.1μm Au
contact material	CuSn alloy		Cu-alloy	
creeping current resistance	KC 175 nach DIN 53480	KC 250		
creepage	1,4mm VDE0110			
air gap	1mm VDE0110			
nominal current	1 A	2 A	1.5 A	
nominal voltage	250V AC insulation group A, according to VDE0110		150 V DC	100 V DC
test voltage	500 V AC			
insertion / drawing force	≥0.3N ... ≤0.7N per contact		≥0.5 ... ≤1.8N per contact	
cycles of operation	≥50 according to DIN 41640	200 to DIN41651		
insulating body material	PC/ colour: RAL 7032		PBT, schwarz	
temperature range	-55°C... +125°C		-40°C... +105°C	
class of inflammability	UL 94 V-0			
specific insulation resistance	> 10 ⁷ Ω·m		> 10 ¹⁰ Ω·m	
cross-section	AWG 28...30 = 0,09...0,05 mm ²			


Technical data: IDC-connectors

	SBAU ... Z	KK ... Z, SBAU 1 ... Z	BK 01 32
surface contact / contact sleeve	Ni+5µm Sn	Ni+5...10µm Sn	
contact material	CuSn alloy		
creeping current resistance	KC 175 nach DIN 53480		
creepage	≥0,7mm VDE 0110		
air gap	≥0,5 mm VDE 0110		
nominal current	1 A		2 A
nominal voltage	250V AC insulation group A, according to VDE0110		300 V _{eff} max.
test voltage	500 V AC		
insulating body material	PC	colour: RAL 7032	
temperature range	-55°C... +125°C		-30°C... +105°C
class of inflammability	UL 94 V-1	UL 94 V-0	
specific insulation resistance	>10 ¹² Ω·m		
conductor			7 x Ø 0,127 mm
cross-section	AWG 28...30 = 0,09...0,05 mm ²		AWG 28/~0,089 mm ²
capacity			≤ 65 pF/m symmetrical
conductor resistance			≤230mΩ/m
characteristic impedance			170 Ω symmetrisch



USB & RJ 45 connectors

- USB 2.0 type A and typ B
- USB 2.0 mini type B
- USB 2.0 micro type B
- USB 3.0 type A
- USB 3.1 type C
- RJ 45



D-Sub connectors

- with Wire Wrap, solder cup and dip soldering connection
- with plastic angle and rivet, earthing plate, snap-in clip
- with metal angle and rivet



D-Sub hoods

- design with large cable space
- hoods with self-cutting threaded bolts
- hoods with quick fastener
- compact hoods with cable outlet on the side



D-Sub accessories

- cable reels
- cut-out covers
- HF-dense seal caps
- HF seals
- Dust covers
- Threaded couplings

USB connectors

USB 2.0 type A sockets


- for PCB mounting
- in THT design
- industrial standard
- * PCB edge (PCB)

				
art. no.	no. of contacts	type	connection type	packing
USB 2 A 90	4	USB Typ A	THT (soldering)	Tray
surface of contact:		selective gold-plated		
				
art. no.	no. of contacts	type	connection type	packing
USB 2 A 90 V	4	USB Typ A	THT (soldering)	Tray
surface of contact:		selective gold-plated		
				
art. no.	no. of contacts	type	connection type	packing
USB 2 A 180	4	USB Typ A	THT (soldering)	Tray
surface of contact:		selective gold-plated		


USB connectors

USB 2.0 type B sockets

- for PCB mounting
- in THT design
- industrial standard
- * PCB edge (PCB)




art. no.	no. of contacts	type	connection type	packing
USB 2 B 90	4	USB Typ B	THT (soldering)	Tray
surface of contact:		selective gold-plated		



art. no.	no. of contacts	type	connection type	packing
USB 2 B 180	4	USB Typ B	THT (soldering)	Tray
surface of contact:		selective gold-plated		

USB 2.0 type B mini sockets

- for PCB mounting
- in THT design
- industrial standard
- * PCB edge (PCB)




art. no.	no. of contacts	type	connection type	packing
USB MN 2 B	5	USB Typ B	THT (soldering)	Tray
surface of contact:		selective gold-plated		

USB connectors


USB 2.0 type A sockets

- for PCB mounting
- in SMD design
- industrial standard
- * PCB edge (PCB)

 				
art. no.	no. of contacts	type	connection type	packing
USB 2 A SMD	4	USB Typ A	SMD	Tray
surface of contact:		selective gold-plated		


USB 2.0 type B sockets

- for PCB mounting
- in SMD design
- industrial standard
- * PCB edge (PCB)

 				
art. no.	no. of contacts	type	connection type	packing
USB 2 B SMD	4	USB Typ B	SMD	Tray
surface of contact:		selective gold-plated		

USB 2.0 type B mini sockets

- for PCB mounting
- in SMD design
- industrial standard
- * PCB edge (PCB)


 				
art. no.	no. of contacts	type	connection type	packing
USB MN 2 B SMD	5	USB Typ B	SMD	Tray
surface of contact:		selective gold-plated		



USB connectors

USB 2.0 type B micro sockets



- for PCB mounting
- in SMD design
- industrial standard
- * PCB edge (PCB)



				
art. no.	no. of contacts	type	connection type	packing
USB MC 2 B SMD	5	USB Typ B	SMD	tape and reel
surface of contact:		selective gold-plated		

USB connectors

USB 3.0 type A sockets

- for PCB mounting
- in THT design
- industrial standard

				
art. no.	no. of contacts	type	connection type	packing
USB 3 A 90	9	USB Typ A	THT (soldering)	Tray
surface of contact:		selective gold-plated		

				
art. no.	no. of contacts	type	connection type	packing
USB 3 A 90 V	9	USB Typ A	THT (soldering)	Tray
surface of contact:		selective gold-plated		

USB 3.1 type C sockets

- for PCB mounting
- in THR / SMD design
- industrial standard

art. no.	no. of contacts	type	connection type	packing
USB 31 C	24	USB Typ C	THR / SMD	tape and reel
surface of contact:		selective gold-plated		

D-Sub high density
D-Sub in SMD technique
D-Sub cut-out cover
D-Sub connectors / flat cable

→ I 13
→ I 27
→ I 32
→ I 14











Screw fastening
D-Sub mixed layout
HF-seals
Technical data

→ I 33
→ I 17
→ I 34
→ I 36 – 38

RJ 45 connectors

RJ 45 sockets

- for PCB mounting
- in THT design
- industrial standard

				
art. no.	no. of contacts	type	connection type	packing
RJ 45 U	10	RJ 45	THT (soldering)	Tray
surface of contact:		selective gold-plated		
				
art. no.	no. of contacts	type	connection type	packing
RJ 45 G	10	RJ 45	THT (soldering)	Tray
surface of contact:		selective gold-plated		
				
art. no.	no. of contacts	type	connection type	packing
RJ 45 LED	8	RJ 45	THT (soldering)	Tray







LED 1: yellow

LED 2: green



surface of contact:	selective gold-plated
----------------------------	-----------------------

D-Sub standard connectors

Male and female headers









	9 - 37 pol. 			50 pol. 					
art. no.	design	dim. [mm]		art. no.	design	dim. [mm]			
		A	B			A	B		
DS 09 T ...	male	30.8	25.0	DS 37 T ...	male	69.5	63.5		
DS 15 T ...		39.2	33.3	DS 50 T ...		67.0	61.1		
DS 25 T ...		53.1	47.0						
	9 - 37 pol. 			50 pol. 					
art. no.	design	dim. [mm]		art. no.	design	dim. [mm]			
		A	B			A	B		
DB 09 T ...	female	30.8	25.0	DB 37 T ...	female	69.5	63.5		
DB 15 T ...		39.2	33.3	DB 50 T ...		67.0	61.1		
DB 25 T ...		53.1	47.0						
please indicate:									
... type of mounting (optional)									
RC M3 = snap-in-clip with M3									
RC UN = snap-in-clip with UNC 4-40									
RCS M3 = snap-in-clip and screwing bolt with M3									
RCS UN = snap-in-clip and screwing bolt with UNC 4-40									

Overview type of mounting (optional)



... RC UN ... RC M3		... RCS UN ... RCS M3	
			

D-Sub standard connectors

Male and female headers

	9 - 37 pol.		50 pol.					
								
art. no.	design	dim. [mm]		art. no.	design	dim. [mm]		
		A	B			A	B	
DS 09 L ...	male	30.8	25.0	DS 37 L ...	male	69.5	63.5	
DS 15 L ...		39.2	33.3	DS 50 L ...		67.0	61.1	
DS 25 L ...		53.1	47.0					
	9 - 37 pol.		50 pol.					
								
art. no.	design	dim. [mm]		art. no.	design	dim. [mm]		
		A	B			A	B	
DB 09 L ...	female	30.8	25.0	DB 37 L ...	female	69.5	63.5	
DB 15 L ...		39.2	33.3	DB 50 L ...		67.0	61.1	
DB 25 L ...		53.1	47.0					
please indicate: ... type of mounting (optional)								
GN M3 = threaded rivet with M3								
GN UN = threaded rivet with UNC 4-40								
GNS M3 = threaded rivet and screwing bolt with M3								
GNS UN = threaded rivet and screwing bolt with UNC 4-40								


Overview type of mounting (optional)

... GN M3 ... GN UN 		... GNS M3 ... GNS UN 	
---	--	--	--

D-Sub standard connectors


Male headers with IP protection

- IP 67 protected
- solder bucket connection

			
art. no.	design	dim. [mm]	
		A	B
DS 09 L IP 67	male	40.0	25.0
DS 15 L IP 67		48.4	33.3
DS 25 L IP 67		62.0	47.0







Female headers with IP protection

- IP 67 protected
- solder bucket connection





			
art. no.	design	dim. [mm]	
		A	B
DB 09 L IP 67	female	40.0	25.0
DB 15 L IP 67		48.4	33.3
DB 25 L IP 67		62.0	47.0

D-Sub standard connectors


Male and female headers

							
art. no.	design	dim. [mm]		art. no.	design	dim. [mm]	
		A	B			A	B
DS 09 WW 3 ...	male	30.8	25.0	DS 37 WW 3 ...	male	69.5	63.5
DS 15 WW 3 ...		39.2	33.3	DS 50 WW 3 ...		67.0	61.1
DS 25 WW 3 ...		53.1	47.0				
							
art. no.	design	dim. [mm]		art. no.	design	dim. [mm]	
		A	B			A	B
DB 09 WW 3 ...	female	30.8	25.0	DB 37 WW 3 ...	female	69.5	63.5
DB 15 WW 3 ...		39.2	33.3	DB 50 WW 3 ...		67.0	61.1
DB 25 WW 3 ...		53.1	47.0				
please indicate: ... type of mounting (optional)							
GN M3 = threaded rivet with M3							
GN UN = threaded rivet with UNC 4-40							
GNS M3 = threaded rivet and screwing bolt with M3							
GNS UN = threaded rivet and screwing bolt with UNC 4-40							



Overview type of mounting (optional)

... GN M3 ... GN UN ... WW 3 ... GN 2,65		... GNS M3 ... GNS UN ... WW 3 ... 5 2,65 GNS Ø 5 M3/UNC 4-40	
			

D-Sub standard connectors with mounting bracket



art. no.	design	fixing part
DS WE 3 ...	male	plastic angle with earthing plate, threaded rivet M3
DS WE 4 ...		plastic angle with earthing plate, threaded rivet UNC 4-40
DB WE 3 ...	female	plastic angle with earthing plate, threaded rivet M3
DB WE 4 ...		plastic angle with earthing plate, threaded rivet UNC 4-40
please indicate: ... no. of contacts 9 15 25 37		



art. no.	design	fixing part
DS WR 3 ...	male	plastic angle with earthing plate, threaded rivet M3, snap-on clip
DS WR 4 ...		plastic angle with earthing plate, threaded rivet UNC 4-40, snap-on clip
DB WR 3 ...	female	plastic angle with earthing plate, threaded rivet M3, snap-on clip
DB WR 4 ...		plastic angle with earthing plate, threaded rivet UNC 4-40, snap-on clip
please indicate: ... no. of contacts 9 15 25 37		

D-Sub connectors High Density

Male and female headers

- our D-Sub connectors **HD** are loaded with turned precision contacts
- with shielding springs





art. no.	no. of contacts	design	dim. [mm]
HD S 15 L ...	15	male	A 30.8 B 25.0
HD S 26 L ...	26		A 39.2 B 33.3
HD S 44 L ...	44		A 53.1 B 47.0
casing frame:		steel, tin plated	
art. no.	no. of contacts	design	dim. [mm]
HD B 15 L ...	15	female	A 30.8 B 25.0
HD B 26 L ...	26		A 39.2 B 33.3
HD B 44 L ...	44		A 53.1 B 47.0
please indicate:		... type of mounting (optional)	
		GN M3 = threaded rivet with M3	
		GN UN = threaded rivet with UNC 4-40	
		GNS M3 = threaded rivet and screwing bolt with M3	
		GNS UN = threaded rivet and screwing bolt with UNC 4-40	
casing frame:		steel, tin plated	

Overview type of mounting (optional)

... GN M3 ... GN UN			... GNS M3 ... GNS UN		
------------------------	--	--	--------------------------	--	--

D-Sub connector for flat ribbon cable

Male and female headers

							
art. no.	no. of contacts	design	dim. [mm]				
DS BK 09	9	male	A	B	C	D	E
DS BK 15	15		30.6	25.0	10.96	17.9	16.1
DS BK 25	25		39.0	33.3	19.33	26.2	23.9
DS BK 37	37		52.8	47.0	33.13	39.9	38.1
DS BK 37	37		69.2	63.5	49.70	56.3	54.7
							
art. no.	no. of contacts	design	dim. [mm]				
DS BK 50	50	male	A	B	C	D	E
DS BK 50	50		66.8	61.1	44.2	54	68.6
							
art. no.	no. of contacts	design	dim. [mm]				
DB BK 09	9	female	A	B	C	D	E
DB BK 15	15		30.6	25.0	10.96	16.3	16.1
DB BK 25	25		39.0	33.3	19.33	24.5	23.9
DB BK 37	37		52.8	47.0	33.13	38.5	38.1
DB BK 37	37		69.2	63.5	49.70	54.8	54.7
							
art. no.	no. of contacts	design	dim. [mm]				
DB BK 50	50	female	A	B	C	D	E
DB BK 50	50		66.8	61.1	44.2	52.4	68.6










D-Sub mixed layout connectors

Order example (case and assembly type)

DSM / DBM	7W2	L	GN	UN
connector	Contact pattern (see overview)	connection type signal contact (L = solder bucket connection)	assembly type (see overview)	internal thread (UNC 4-40)
(DSM = D-Sub male header mixed layout DBM = D-Sub female header mixed layout)	case		assembly type (optional)	

Overview contact pattern

- the contact pattern is valid for male headers
- for using socket connectors the hole pattern has to be mirrored

 ... 2W2C ...	 ... 3W3 ...	 ... 5W5 ...	 ... 8W8 ...
	 ... 7W2 ...	 ... 9W4 ...	 ... 21WA4 ...
		 ... 13W3 ...	 ... 25W3 ...
		 ... 17W2 ...	 ... 27W2 ...

Order example (mixed layout contacts)


HAS	10	TA
high-power contacts (HAS = high-power contacts male)	current (10 A)	connection type mixed layout contacts (see overview)
mixed layout contacts		

Overview mixed layout contacts, connection type

	solder bucket connection straight ... L	crimp connection straight ... C	PCB connection angled ... TA
male			
female			

D-Sub mixed layout connectors






Overview assembly type (optional)








D-Sub mixed layout connectors


Male headers

- gold-plated contacts, straight
- equipped with turned precision contacts
- for power cables up to AWG 16
- combinable with high-power contacts **HAS ...** → I 25

	
art. no. DSM 2W2C L ...	design male signal contacts 0 high-power contacts max. 2
	
art. no. DSM 3W3 L ...	design male signal contacts 0 high-power contacts max. 3
	
art. no. DSM 5W5 L ...	design male signal contacts 0 high-power contacts max. 5
	
art. no. DSM 7W2 L ...	design male signal contacts 5 high-power contacts max. 2
	
art. no. DSM 8W8 L ...	design male signal contacts 0 high-power contacts max. 8
please indicate: ... type of mounting (optional) GN M3 = threaded rivet with M3 GN UN = threaded rivet with UNC 4-40 GNS M3 = threaded rivet and screwing bolt with M3 GNS UN = threaded rivet and screwing bolt with UNC 4-40	
casing frame:	steel, tin plated

			
art. no. DSM 9W4 L ...	design male	signal contacts 5	high-power contacts max. 4
			
art. no. DSM 13W3 L ...	design male	signal contacts 10	high-power contacts max. 3
			
art. no. DSM 17W2 L ...	design male	signal contacts 15	high-power contacts max. 2
			
art. no. DSM 21WA4 L ...	design male	signal contacts 17	high-power contacts max. 4
			
art. no. DSM 25W3 L ...	design male	signal contacts 22	high-power contacts max. 3
please indicate: ... type of mounting (optional) GN M3 = threaded rivet with M3 GN UN = threaded rivet with UNC 4-40 GNS M3 = threaded rivet and screwing bolt with M3 GNS UN = threaded rivet and screwing bolt with UNC 4-40			
casing frame:		steel, tin plated	





D-Sub mixed layout connectors

			
art. no.	design	signal contacts	high-power contacts
DSM 27W2 L ...	male	25	max. 2
please indicate: ... type of mounting (optional) GN M3 = threaded rivet with M3 GN UN = threaded rivet with UNC 4-40 GNS M3 = threaded rivet and screwing bolt with M3 GNS UN = threaded rivet and screwing bolt with UNC 4-40			
casing frame:	steel, tin plated		

D-Sub mixed layout connectors

Male headers






- gold-plated contacts, angled
- equipped with turned precision contacts
- with PCB connection, angled
- combinable with high-power contacts **HAS ...** → I 25






			
art. no. DSM 7W2 TA ...	design male	signal contacts 5	high-power contacts max. 2
			
art. no. DSM 9W4 TA ...	design male	signal contacts 5	high-power contacts max. 4
			
art. no. DSM 13W3 TA ...	design male	signal contacts 10	high-power contacts max. 3
			
art. no. DSM 17W2 TA ...	design male	signal contacts 15	high-power contacts max. 2
please indicate: ... type of mounting (optional) MW M3 = metal angle with M3 MW UN = metal angle with UNC 4-40 MWS M3 = metal angle screwing bolt with M3 MWS UN = metal angle and screwing bolt with UNC 4-40			
casing frame:		steel, tin plated	

D-Sub mixed layout connectors


Female headers

- gold-plated contacts
- equipped with turned precision contacts
- for power cables up to AWG 16
- combinable with high-power contacts **HAB ... → I 26**

			
art. no. DBM 2W2C L ...	design female	signal contacts 0	high-power contacts max. 2
			
art. no. DBM 3W3 L ...	design female	signal contacts 0	high-power contacts max. 3
			
art. no. DBM 5W5 L ...	design female	signal contacts 0	high-power contacts max. 5
			
art. no. DBM 7W2 L ...	design female	signal contacts 5	high-power contacts max. 2
			
art. no. DBM 8W8 L ...	design female	signal contacts 0	high-power contacts max. 8
please indicate: ... type of mounting (optional) GN M3 = threaded rivet with M3 GN UN = threaded rivet with UNC 4-40 GNS M3 = threaded rivet and screwing bolt with M3 GNS UN = threaded rivet and screwing bolt with UNC 4-40			
casing frame:		steel, tin plated	

			
art. no. DBM 9W4 L ...	design female	signal contacts 5	high-power contacts max. 4
			
art. no. DBM 13W3 L ...	design female	signal contacts 10	high-power contacts max. 3
			
art. no. DBM 17W2 L ...	design female	signal contacts 15	high-power contacts max. 2
			
art. no. DBM 21WA4 L ...	design female	signal contacts 17	high-power contacts max. 4
			
art. no. DBM 25W3 L ...	design female	signal contacts 22	high-power contacts max. 3
please indicate: ... type of mounting (optional) GN M3 = threaded rivet with M3 GN UN = threaded rivet with UNC 4-40 GNS M3 = threaded rivet and screwing bolt with M3 GNS UN = threaded rivet and screwing bolt with UNC 4-40			
casing frame:		steel, tin plated	





D-Sub mixed layout connectors

							
art. no.		design		signal contacts		high-power contacts	
DBM 27W2 L ...		female		25		max. 2	
please indicate: ... type of mounting (optional)							
GN M3 = threaded rivet with M3							
GN UN = threaded rivet with UNC 4-40							
GNS M3 = threaded rivet and screwing bolt with M3							
GNS UN = threaded rivet and screwing bolt with UNC 4-40							
casing frame:				steel, tin plated			

D-Sub mixed layout connectors

Female headers

- gold-plated contacts, angled
- equipped with turned precision contacts
- with PCB connection, angled
- combinable with high-power contacts **HAB ...** → I 26


			
art. no. DBM 7W2 TA ...	design female	signal contacts 5	high-power contacts max. 2
			
art. no. DBM 9W4 TA ...	design female	signal contacts 5	high-power contacts max. 4
			
art. no. DBM 13W3 TA ...	design female	signal contacts 10	high-power contacts max. 3
			
art. no. DBM 17W2 TA ...	design female	signal contacts 15	high-power contacts max. 2
please indicate: ... type of mounting (optional) MW M3 = metal angle with M3 MW UN = metal angle with UNC 4-40 MWS M3 = metal angle screwing bolt with M3 MWS UN = metal angle and screwing bolt with UNC 4-40			
casing frame:		steel, tin plated	

High-power contacts, loose


Pin contacts

- 10 A / 20 A / 40 A
- combinable with cases **DSM ...** → I 17-I 20


– straight, with solder bucket connection

			
	art. no.	current [A]	dim. [mm]
HAS 10 L	10	1.8	2.55
HAS 20 L	20	2.8	3.70
HAS 40 L	40	4.8	5.60

– straight, with connection crimp

			
	art. no.	current [A]	dim. [mm]
HAS 10 C	10	1.8	2.55
HAS 20 C	20	2.8	3.70
HAS 40 C	40	4.8	5.60


– angled, with PCB connection (tin-plated)

			
	art. no.	current [A]	dim. [mm]
HAS 10 TA	10	1.8	2.55
HAS 20 TA	20	2.8	3.70
HAS 40 TA	40	4.8	5.60


Socket contact

- 10 A / 20 A / 40 A
- combinable with cases **DBM ...** → I 21-I 24

- straight, with solder bucket connection


			
	art. no.	current [A]	dim. [mm]
HAB 10 L	10	A	B
HAB 20 L	20	1.8	2.55
HAB 40 L	40	2.8	3.70
		4.8	5.60

- straight, with connection crimp

			
	art. no.	current [A]	dim. [mm]
HAB 10 C	10	A	B
HAB 20 C	20	1.8	2.55
HAB 40 C	40	2.8	3.70
		4.8	5.60

Socket contact


- angled, with PCB connection (tin-plated)


			
	art. no.	current [A]	dim. [mm]
HAB 10 TA	10	A	B
HAB 20 TA	20	1.8	2.55
HAB 40 TA	40	2.8	3.70
		4.8	5.60

D-Sub in SMD-mounting

Male and female headers



– packing: tape and reel (150 pcs/reel); reel outer diameter 330 mm

					
art. no.	no. of contacts	dim. [mm]			
DS 09 SMD TR	9	A	B	Y	Z
DS 15 SMD TR	15	30.8	25.0	10.98	1.37
DS 25 SMD TR	25	39.2	33.3	19.20	1.38
DS 37 SMD TR	37	53.1	47.0	33.12	
DS 37 SMD TR	37	69.5	63.5	49.68	1.38

					
art. no.	no. of contacts	dim. [mm]			
DB 09 SMD TR	9	A	B	Y	Z
DB 15 SMD TR	15	30.8	25.0	10.98	1.37
DB 25 SMD TR	25	39.2	33.3	19.20	1.38
DB 37 SMD TR	37	53.1	47.0	33.12	
DB 37 SMD TR	37	69.5	63.5	49.68	1.38

D-Sub hoods



- **E** = max. diameter of the cable entry in mm
- threaded bolt UNC 4-40
- large cable space with few components
- **9-37 contacts can be mounted in series in (C = 3 HP) grid, thus especially suitable for 19" technology**

						
art. no.	no. of contacts	dim. [mm]				
		A	B	C	D	E
DH 09 ...	9	31.5	25	15.2	31	8.5
						
art. no.	no. of contacts	dim. [mm]				
		A	B	C	D	E
DH 15 ...	15	40.0	33.3	15.2	33.5	8.5
DH 25 ...	25	53.5	47.0		38.0	11.0
DH 37 ...	37	70.0	63.5		40.0	
DH 50 ...	50	67.5	61.1	18.2		40.0
please indicate: ... surface of case						
S = plastic, black						
M = plastic, metallized						

D-Sub hoods




IP 67 protected

– straight cable outlet with pre-assembled strain relief

					
art. no.	dim. [mm]				
	A	B	C	D	
DH 09 L IP 67	40.8	77	25.00	10	
DH 15 L IP 67	49.5	79	33.30	12	
DH 25 L IP 67	63.0	87	47.04		

D-Sub hoods with quick-action locking system

– straight and side-gated cable outlet

						
art. no.	no. of contacts	dim. [mm]				
		A	B	C		
DH SV 09 ...	9	33.0	25.0	15.4		
DH SV 15 ...	15	41.3	33.3			
DH SV 25 ...	25	55.0	47.0			
DH SV 37 ...	37	71.5	63.5	18.4		
DH SV 50 ...	50	69.1	61.1			
please indicate: ... surface of case S = plastic, black M = plastic, metallized						

Accessories – locking pin for hood – hood connection

– 2 locking pins including locking plates

art. no.	
RS HH	

D-Sub hoods

Accessories – locking pin for plug connector – hood connection

– 2 latch Pins including locking ring for connectors with thread M3/UNC 4-40

art. no.	type of thread	art. no.	type of thread
RS SH 3	M3	RS SH 4	UNC 4-40

Accessories – locking pin for plug connector – hood connection

– 2 locking pins including spring washer, washer and nut for exisiting connector with through hole

art. no.			
RS SH D			

Cable sleeve - quick-release hood DH SV ...

– cable sleeves are supplied with chamfers, which are adequate to a diameter-grading of 0.5 mm; they can be cut off depending on the exisiting diameter of the cable.
– for cable diameters 3...9 mm

art. no.	no. of contacts		
KT SV	9		


D-Sub hoods

D-Sub-hoods-compact

9-50 contacts





- width C - 3 HP
- version 9-37 pins can be mounted in series in 3 HP grid, thus especially suitable for 19" technology
- metallized version with excellent shielding against electrical and magnetic alternating fields
- integrated dust protective shroud
- captive latching screws with UNC 4-40 threads
- 2 side cable outputs:
 - 40° exit (9-50 contacts)
 - 90° exit (25-50 contacts)
- **E** = max. diameter of the cable bushing in mm

						
art. no.	no. of contacts	dim. [mm]				
		A	B	C	D	E
DH 09 ...	9	31.5	25.0	15.2	37	8.5
DH 15 ...	15	40.0	33.3		41	11.0
DH 25 ...	25	53.5	47.0			
DH 37 ...	37	70.0	63.5	18.2		12.0
DH 50 ...	50	67.8	61.1			
please indicate: ... surface of case						
K = plastic, black						
KM = plastic, metallized						

D-Sub accessories




Suitable cable bushing

– protects the cable against damage by buckling




	 KT 0915	 KT 2550	
art. no.	for no. of contacts	art. no.	for no. of contacts
KT 0915	9/ 15	KT 2550	25/ 37/ 50

Cover for D-Sub cut outs in front and back panel

- suitable for EMC application, closed on one side
- blank covers for exact sealing of unused D-Sub cut outs in front- and backpanels, size and form are like D-Sub housings

							
art. no.	dim. [mm]						
	A		B		C		D
BADM 09	30.8		25.0		19.2		16.3
BADM 15	39.3		33.3		27.5		24.5
BADM 25	53.0		47.0		41.2		38.3
BADM 37	69.4		63.5		57.7		54.8
casing frame:		tin-plated					

- plastic cover, blank, for blind D-Sub and other connector cutouts in front and rear panels
- simple mounting by clamping

			
art. no.	dim. [mm]		
	A	B	C
BADK 09	32.0	25.0	14.0
BADK 15	40.3	33.3	
BADK 25	54.0	47.0	
BADK 37	70.5	63.5	
BADK 50	68.1	61.1	16.6

D-Sub accessories


Screw fastening, mounted

- 2 screw fastenings incl. spacer, washer, nut
- please add a **V** to the corresponding art. no. ...

art. no.	
... V	


Screw fastening, loose

- 2 separate screw fasteners, with washer and nut

art. no.		
V 2		
material:	screw - brass nickel-plated/ screw-nut - steel nickel-plated/ steel-washer galvanized	


Screw fastening for assembly of cases, separate

- 2 screw fastenings incl. spacer, washer, nut

art. no.		
VG 2		
material:	steel-washer tin-plated/ screw and steel-screw-nut verzinkt	


HF-tight caps, male and female headers

– prevent HF-radiation at open interfaces

							
art. no.	design	colour	dim. [mm] A	art. no.	design	colour	dim. [mm] A
HFK S 09	male	blue	32.9	HFK B 09	female	red	32.9
HFK S 15			41.3	HFK B 15			41.3
HFK S 25			55.7	HFK B 25			55.7
annotation:			internal 50 µm electromagnetical protective coating				


HF-seals

– as seal between plug and housing


			
art. no.	dim. [mm]		
	A		B
HFD 09	30.8		25.0
HFD 15	39.4		33.3
HFD 25	53.4		47.0
HFD 37	70.7		63.5
annotation:		extremely low transition resistance	

Dust protection caps

For male headers

			
art. no.	dim. [mm]		
	A	B	
SSK S 09	22.5	18.2	
SSK S 15	30.6	26.5	
SSK S 25	43.7	39.8	
SSK S 37	60.3	56.2	

For female headers

			
art. no.	dim. [mm]		
	A	B	
SSK B 09	22.3	17.00	
SSK B 15	30.6	25.00	
SSK B 25	44.1	38.65	
SSK B 37	60.7	55.30	
annotation:		extremely low transition resistance	

	USB 2 A 180, USB 2 A 90, USB 2 A 90 V, USB 2 A SMD, USB 2 B 90, USB 2 B SMD	USB 2 B 180	USB MN 2 B, USB MN 2 B SMD	USB MC 2 B SMD
contact material	CuSn alloy			
surface contact / contact sleeve	Ni+≥0.2μm Au (selective)			
cycles of operation	1500		5000	10000
nominal current	0.5 A			1 A for Pin 1-5 / 1.8 A for Pin 1, 5 / 0.5 A for Pin 2-4
nominal voltage	40 V _{RMS} /V _{DC}			
insulating body material		PA, white		
temperature range	-25°C ... +85°C (230°C / 5s)		-40°C ... +105°C (260°C / 10s)	-30°C ... +80°C (260°C / 10s)
class of inflammability	UL 94 V-0			
	USB 3 A 90, USB 3 A 90 V	USB 31 C	RJ 45 G, RJ 45 U	RJ 45 LED
contact material	CuSn alloy			
surface contact / contact sleeve	Ni+≥0.2μm Au (selective)			
cycles of operation	1500	10000	750	
nominal current	0.5 A	5 A for VBUS Pin / 1.25 A for VCONN Pin	1 A	
nominal voltage	40 V _{RMS} /V _{DC}		125 V _{RMS} /V _{DC}	
insulating body material				
temperature range	-25°C ... +85°C (230°C / 5s)		-55°C ... +105°C (230°C / 5s)	0°C ... +70°C (230°C/5s)
class of inflammability	UL 94 V-0			
	DB ... L IP 67, DS ... L IP 67	DS ..., DB ...	HD B ..., HD S ...	DS BK ..., DB BK ...
contact material	Cu-alloy			
surface contact / contact sleeve	hard gold plated over nickel			
quality class / cyces of operation	quality class 2 = 200 cycles of operation			quality class 3 = 50 cycles of operation
volume resistance		≤10 mΩ before strain, ΔR 10 mΩ after strain according to DIN 41652. part 2 (MIL- C-24308)		≤10 mΩ
air gap and creep distance		cont.-contact <1mm/ contact-earth <1mm	cont.-contact <0.6mm/ contact- earth <0.6mm	<0.9mm according to VDE0110
nominal current	5A (20°C)		3A (20°C)	1A at AWG 28/ 1.5A at AWG 26
nominal voltage	125 V AC	125 V DC	60 V AC	
test voltage	1000 V			1000 V DC
insulating body material	PBT, GF			PBTP, GF
temperature range	-55°C... +125°C			
class of inflammability	UL 94 V-0			
insulation resistance	≥5 GΩ			1 GΩ

Technical data: USB / RJ / D-Sub connectors

	DBM ..., DBM ... TA, DSM ..., DSM ... TA	HAB ... C, HAB ... L, HAS ... C, HAS ... L	HAB ... TA, HAS ... TA	DH ... L IP 67
contact material	Cu-alloy			
surface contact / contact sleeve	nickel-phosphorus- gold-surface/ (≥0.1μm Au over 2...4μm chem. NiP)	Ni+ ≥0.2μm Au	Ni+ ≥0.2μm Au (se- lective)	
quality class / cyces of operation	quality class 2 = 200 cycles of operation			
nominal current	signal contact: ≤5 A/ power contact: ≤20 A	power contact: ≤20 A		
nominal voltage	125 V AC			
test voltage	1000 V			
insulating body material	Polyester, GF			ABS
temperature range	-55°C... +125°C	-55°C... +150°C		
class of inflammability	UL 94 V-0			UL 94 V-0
surface of case				plastic, black
insulation resistance	≥5 GΩ			
	DH ... S, DH ... M, DH SV ...	KT SV	DH ... K DH ... KM	BADM ...
insulating body material	ABS	EPTR	ABS	
class of inflammability	UL 94 V-0	UL 94 V-0 (at thickness ≥3mm), UL 94 V-1	UL 94 V-0	
surface of case	plastic, black/ plastic, metallized		plastic, black/ plastic, metallized	metal

	BADK ...	HFK S ... HFK B ...	HFD ...	SSK S ... SSK B ...
insulating body material	ABS		Silicone, filled with silver-plated copper particles	Polyethylene
temperature range		-35°C ... +85°C		
class of inflammability	UL 94 V-0			
surface of case	plastic, grey			




Brackets for PCI

- with or without fixing tab
- standard cut-outs
- custom-specific cut-outs
- custom-specific printings




Brackets for AT and similar

- with or without fixing tab
- standard cut-outs
- custom-specific cut-outs
- custom-specific printings



Custom-specific brackets

- double width
- special width
- with printing




Equipped brackets

- equipped with D-Sub
- equipped with LED
- equipped with custom-specific components

Index Bracket-Groups

page	PCI	7		9			12	13	14		15		17	18
	KHPC	8	9	10	11	11	12	13	14	15	15	16	17	18

page	PCI	18			21		21		22		23		
	KHPC	19	20	20		21		22	22	23		24	24



Brackets with fixing strap and without cutout

PCI PCI ... L	KHPC KHPC ... L
art. no. PCI 0 L	art. no. KHPC 0 L


Bracket without fixing strap and without cutout

PCI PCI ... O	KHPC KHPC ... O
art. no. PCI 0 O	art. no. KHPC 0 O
material: material thickness:	stainless steel (V 2 A) 0.8 mm


Low Profile bracket for PC

Low Profile bracket with fixing strap and without cutout


- with or without fixing tap; standard cutouts
- customer-specific cutouts and printing; double width (special widths) on request



Low Profile bracket without fixing strap and without cutout




Dimensional drawing for PCBs



Dimensions to fix the PCI L ... - bracket to the PCB




Dimensions to fix the KHPC L ... - bracket to the PCB



On request also available with D-Sub connector!

Retainers for PCI-cards

– suitable for all ISA-versions



art. no.	
PCI R1	
class of inflammability:	UL 94 V-0
material:	polycarbonate

B

C

D

E

F

G

Н

1

K












L

M

N

K 7

If you do not find a suitable bracket, please use the PCI / KHPC design sheet at the end of section "K".

	KHPC 002 O 	KHPC 003 ... 	KHPC 007 O 
KHPC 011 O 	KHPC 013 O 	KHPC 010 ... 	KHPC 093 L 
KHPC 094 O 	KHPC 096 O 	KHPC 008 O 	KHPC 014 O 

please indicate:

... fixing strap

O = without fixing strap

L = with fixing straps

		KHPC 016 O	KHPC 095 O	KHPC 017 ...
B				
C				
D				
E				
F				
G				
H				
I				
K				
L				
M				

PCI 041 ...	PCI 012 ...		
	KHPC 144 O	KHPC 142 O	KHPC 053 O
KHPC 138 O	KHPC 006 O	KHPC 012 O	KHPC 141 O









please indicate:

... fixing strap

O = without fixing strap

L = with fixing straps

KHPC 072	KHPC 009 O	KHPC 143 O	KHPC 015 L
	KHPC 160 O		
	KHPC 065 O	KHPC 454 O	KHPC 005 O









	PCI 065 O 	PCI 031 O 	PCI 032 O 
	KHPC 179 O 	KHPC 177 O 	KHPC 178 O 
KHPC 076 O 			

please indicate:

... fixing strap

O = without fixing strap

L = with fixing straps

	PCI 033 ... 		
	KHPC 189 L 	KHPC 041 O 	KHPC 040 O 
KHPC 185 O 	KHPC 061 O 	KHPC 038 O 	KHPC 187 O 











KHPC 188 O	KHPC 078 O		
	PCI 014 L	PCI 045 ...	PCI 015 ...
	KHPC 019 O	KHPC 073 ...	KHPC 024 O

please indicate:

... fixing strap

O = without fixing strap

L = with fixing straps

 15	KHPC 200 O 	KHPC 455 L 	KHPC 218 O 
 15 15	PCI 047 O 	PCI 071 O 	
 15 15	KHPC 230 O 	KHPC 022 L 	KHPC 225 O 













KHPC 069 O	KHPC 229 O	KHPC 018 O	
	KHPC 042 O	KHPC 241 O	KHPC 242 O
KHPC 075 O			








please indicate:

... fixing strap

O = without fixing strap

L = with fixing straps

	PCI 017 ... 	PCI 018 ... 	PCI 016 L 
	KHPC 243 O 	KHPC 070 O 	KHPC 027 O 
KHPC 054 O 	KHPC 028 O 	KHPC 026 ... 	KHPC 052 L 









	PCI 072 O 		
	KHPC 262 O 	KHPC 043 O 	
	PCI 076 O 	PCI 035 L 	PCI 077 ... 

please indicate:

... fixing strap

O = without fixing strap

L = with fixing straps

PCI 020 ...			
			
KHPC 058 O	KHPC 035 O	KHPC 277 O	
			
KHPC 267 O	KHPC 033 O	KHPC 270 O	KHPC 271 O
			

KHPC 034 O	KHPC 031 O	KHPC 032 O	
	KHPC 029 O	KHPC 295 O	
	KHPC 036 ...	KHPC 051 O	KHPC 308 L






please indicate:






... fixing strap

O = without fixing strap

L = with fixing straps

Brackets for PC







	PCI 021 O			
				
	KHPC 325 O			
				
	PCI 083 L			
				








	KHPC 335 L		
			
	PCI 104 O		
			
	KHPC 365 L		
		KHPC 085 L	
			KHPC 391 O
			

please indicate:

... fixing strap
O = without fixing strap
L = with fixing straps

Brackets for PC

KHPC 398 O  Technical drawing of the KHPC 398 O bracket. It is a long, narrow vertical bracket with a central slot. Dimensions: total length 90, top flange width 3.5, bottom flange width 11.5, and bottom flange height 21.75.			
 Technical drawing of the KHPC 404 L bracket. It is a long, narrow vertical bracket with two rectangular slots. Dimensions: total length 70.45, distance between slots 15.2, and slot width 13.5.	KHPC 404 L  Technical drawing of the KHPC 404 L bracket. It is a long, narrow vertical bracket with two rectangular slots. Dimensions: total length 70.45, distance between slots 15.2, slot width 13.5, and slot height 13.1.	KHPC 407 L  Technical drawing of the KHPC 407 L bracket. It is a long, narrow vertical bracket with two rectangular slots. Dimensions: total length 54.97, distance between slots 15.8, slot width 13.2, and slot height 2.4.	
 Technical drawing of the PCI 051 ... bracket. It is a long, narrow vertical bracket with four rectangular slots. Dimensions: total length 89.4, distance between slots 13.0, slot width 11.6, and slot height 4.	PCI 051 ...  Technical drawing of the PCI 051 ... bracket. It is a long, narrow vertical bracket with four rectangular slots. Dimensions: total length 89.4, distance between slots 13.0, slot width 11.6, and slot height 4.		

	KHPC 439 O		
			
	KHPC 449 O		
			
	KHPC 469 O		
			
	Detail - B		
			

please indicate:

- ... fixing strap
- O = without fixing strap
- L = with fixing straps

A

B

The cutouts shown on the Design sheet should be positioned on the pictured grid.

The zero point of the respective cutout is to be placed on the grid point of the PC card bracket, whereby the X/Y coordinates should be entered in the table as absolute dimensions. Positioning of the cutouts can be specified with an accuracy of max. 0,01 mm. The grid specifies the max. area of the cutout including the component. Please mark whether the version is with or without bent fixing tabs.

Other contours, dimensions and cutouts are possible, to the extent that they are technically possible to produce.


Please contact us with regard to this.

C

Example

D


PCI



Shape			X-dimension	Y-dimension
A	A = 20	B = 10	14	12
E	D = 5		49	9
D1	D = 12	D1 = 11	65	10

H

KHPC

















Shape			X-dimension	Y-dimension
A	A = 33	B = 10	12	3
E	D = 5		54	9
D1	D = 9,5	D1 = 8,7	68	9


L

M

N



radius F 1 ... 4
build in mode:
☐ 3,4 mm rear
☐ 2,1 mm front

















☐ with fixing strap


☐ without fixing strap

[illegible]

PCI DESIGN



radius F 1 ... 4
build in mode:
☐ 3,4 mm rear
☐ 2,1 mm front




☐ with fixing strap

☐ without fixing strap

[illegible]

PCI DESIGN







☐ with fixing strap☐ without fixing strap

radius F 1 ... 4


build in mode:

☐ 3,4 mm rear

☐ 2,1 mm front



shape: B
with radius, mm:


[illegible]

**KHPC
DESIGN**




Mounting material

- spacers for standard LEDs
- class of flammability acc. to UL 94 VO



LED fastener for horizontal PCB mounting

- single and double fasteners for a standard diameter of 3 and 5 mm
- equipped multi-fastener
- single fasteners and fasteners connectable in series



Fibre-optics for SMD-LED components

- horizontal, fixed fibre-optics with round or rectangular lense made of transparent plastics – also for gauge displays
- vertical, fixed fibre-optics with round or rectangular lense made of transparent plastics





LED fastener for front panel mounting

- clipable fastener for 5 mm LEDs
- fastener for 3 and 5 mm LED with clamping ring

Spacers for LED



– universal mount for LED Ø 3 mm and 5 mm, self retaining

					
art. no.	B [mm]	dim. [mm] A	art. no.	B [mm]	dim. [mm] A
MAH 31	1.5	3.1	MAH 71	4.7	7.1
MAH 41		4.1	MAH 81		8.1
MAH 51		5.1	MAH 89		8.9
MAH 61		6.1	MAH 99	7.9	9.9
insulating body material:		MPPS, black			
temperature range:		-40°C...+240°C/ (260°C/5 s)			
class of inflammability:		UL 94 V-0			



			
art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A
MAH 401	1	MAH 406	6
MAH 402	2	MAH 407	7
MAH 403	3	MAH 408	8
MAH 404	4	MAH 409	9
MAH 405	5	MAH 410	10
insulating body material:		PVC Blend, black	
temperature range:		-40°C... +85°C	
class of inflammability:		UL 94 V-0	

Spacers for LED

– for LED Ø 3 mm, thin mount



					
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A		A
MAH 301	1	MAH 305	5	MAH 308	8
MAH 302	2	MAH 306	6	MAH 309	9
MAH 303	3	MAH 307	7	MAH 310	10
MAH 304	4				
insulating body material:		PVC Blend, black			
temperature range:		-40°C... +85°C			
class of inflammability:		UL 94 V-0			

– for LED Ø 5 mm, self-retaining

					
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A		A
MAH 501	1	MAH 504	4	MAH 508	8
MAH 502	2	MAH 505	5	MAH 509	9
MAH 503	3	MAH 506	6	MAH 510	10
insulating body material:		PVC Blend, black			
temperature range:		-40°C... +85°C			
class of inflammability:		UL 94 V-0			



Spacers for LED

– for rectangular LED



					
art. no.	dim. [mm]	art. no.	dim. [mm]	art. no.	dim. [mm]
	A		A		A
RAH 503	3	RAH 506	6	RAH 509	9
RAH 504	4	RAH 507	7	RAH 510	10
RAH 505	5	RAH 508	8		
insulating body material:		PVC Blend, black			
temperature range:		-40°C... +85°C			
class of inflammability:		UL 94 V-0			

LED-holders



- suitable for 3 mm diodes with a collar height of 0.6 mm
- **K** = cathode

		
art. no.	type	
DH 3 V	for LED Ø3mm	
insulating body material:	PA, GF	

- suitable for 5 mm diodes with a collar height of 0.6 mm/1 mm
- **K** = cathode

		
art. no.	type	
DH 5 VC	for LED Ø5mm	
insulating body material:	PA, GF	









- suitable for 5 mm diodes with a collar height of 0.6 mm/1 mm
- **K** = cathode

		
art. no.	type	
DH 5 SRC	for LED Ø5mm	
insulating body material:	PA, GF	

LED-holders

LED-holder for LED Ø 3 mm and 5 mm








– K = cathode / * = presentation with diode

		
art. no.	type	
DH 3 W	for LED Ø3mm	
		
art. no.	type	
DH 5 W	for LED Ø5mm	
		
art. no.	type	
DH 3 R	for LED Ø3mm	
		
art. no.	type	
DH 5 R	for LED Ø5mm	
insulating body material:	PA 4.6. GF	
temperature range:	-40°C... +163°C/ (260°C/10 s)	
class of inflammability:	UL 94 V-0	

LED-holders

LED-holder for LED Ø 3 mm


– stackable LED-holders: single holder/can be strung, left/can be strung, middle/can be strung, right

	
art. no.	type
DDH 3 E	for LED Ø3mm
	
art. no.	type
DDH 3 L	for LED Ø3mm, can be strung left
	
art. no.	type
DDH 3 M	for LED Ø3mm, can be strung middle
	
art. no.	type
DDH 3 R	for LED Ø3mm, can be strung right
insulating body material:	PA 6/6, GF
temperature range:	-20°C... +85°C
class of inflammability:	UL 94 V-0

LED-holders

Fourfold-LED-holders

- standard case, standard colours, diffuse lens, space-saving design, round lens, rectangular lens
- typical data at $T_{amb}=25^{\circ}\text{C}$ und $I_F=I_{Ftype}$, 100% DC



art. no.	type	emission colour	Spannungen $U_{f_{typ}}$ / U_{rmax} [V]	wavelength λ_{max} [nm]
DLH 21 AYEh	with LED Ø2mm, four-fold	yellow	2.1 / 2.6	585
DLH 21 AGEh		green	2.2 / 2.6	565
insulating body material:		Nylon, black		
temperature range:		-20°C... +85°C		
class of inflammability:		UL 94 V-0		
beam angle 2 φ:		80 °		
design:		2mm round		
for cases:		in terms of colour diffuse		
derating:		from $T_{amb} < 20^{\circ}C$, operating current reduced by 0.4 mA/K .		
light intensity I:		12 mcd		
flows I_{Ftyp} / I_{Fmax}:		20/30 mA		


Light pipes for SMDs

- suitable for current SMD types
- 3 mm light pipes
- horizontal
- ESD-protection from panel to PCB



art. no. LL 30 HRS	diameter of lense way of fixation
art. no. LL 30 HRP	diameter of lense way of fixation
art. no. LL 35 HVS	diameter of lense way of fixation
art. no. LL 30 WRFP 038 LL 30 WRFP 050 LL 30 WRFP 076 LL 30 WRFP 102	diameter of lense way of fixation dim. [mm] A B
insulating body material: temperature range: class of inflammability:	Polycarbonate, clear -30°C... +100°C UL 94 V-0




Light pipes for SMDs


– panel light pipe, 6 mm lens, suitable for common SMD LEDs, white lens, large angle of radiation

			
art. no.	diameter of lense	way of fixation	dim. [mm] A
LL 60 WRB 254	Ø6mm	by press-in pins	25.4

– panel light pipe 3 mm, ESD protection from panel to PCB


	  				
art. no.	diameter of lense	dim. [mm] A	art. no.	diameter of lense	dim. [mm] A
LL 30 PRB 032	Ø3mm	3.2	LL 30 PRB 089	Ø3mm	8.9
LL 30 PRB 064		6.4			

	  				
art. no.	diameter of lense	dim. [mm] A	art. no.	diameter of lense	dim. [mm] A
LL 30 PRL 032	Ø3mm	3.2	LL 30 PRL 127	Ø3mm	12.7
LL 30 PRL 064		6.4	LL 30 PRL 159		15.9
LL 30 PRL 089		8.9			


					
art. no.	diameter of lense	dim. [mm] A	art. no.	diameter of lense	dim. [mm] A
LL 30 PRE 032	Ø3mm	3.2	LL 30 PRE 095	Ø3mm	9.5
LL 30 PRE 064		6.4	LL 30 PRE 127		12.7
insulating body material:		Polycarbonate, clear			
temperature range:		-30°C... +100°C			
class of inflammability:		UL 94 V-0			

Light pipes for SMDs


– panel light pipe 5 mm, ESD protection from panel to PCB

					
art. no.	diameter of lense	dim. [mm] A	art. no.	diameter of lense	dim. [mm] A
LL 50 PRK 032	Ø5mm	3.2	LL 50 PRK 095	Ø5mm	9.5
LL 50 PRK 064		6.4	LL 50 PRK 127		12.7
insulating body material:		Polycarbonate, clear			
temperature range:		-30°C... +100°C			
class of inflammability:		UL 94 V-0			

– panel light pipe Rechteck 3,3 mm, ESD protection from panel to PCB

							
art. no.		diameter of lense	dim. [mm] A	art. no.		diameter of lense	dim. [mm] A
LL 30 QRL 032		□ 3,3mm	3.2	LL 30 QRL 095		□ 3,3mm	9.5
LL 30 QRL 064			6.4	LL 30 QRL 127			12.7
insulating body material:			Polycarbonate, clear				
temperature range:			-30°C... +100°C				
class of inflammability:			UL 94 V-0				

– suitable for current SMD LEDs, vertical, rigid light pipe Ø 3 mm, ESD protection from panel to PCB

			
art. no.	diameter of lense	way of fixation	dim. [mm] A
LL 30 VRFS 024	Ø3mm	by alignment pins	2.4
LL 30 VRFS 050			5.0
LL 30 VRFS 075			7.5
insulating body material:		Polycarbonate, clear	
temperature range:		-30°C... +100°C	
class of inflammability:		UL 94 V-0	

A

B

C

D

E

F

G

H

I

K

L

M

N



OBERFLÄCHEN- VEREDELUNG GMBH

High quality surface treatment for electronic components



Gold-plating

properties:

high resistance to wear, good corrosion resistance, temperature stability and solderability

process:

drum technology

materials:

non-ferrous metals

coating system:

copper/nickel/gold



Tin-plating

properties:

solderable layers with improved tarnishing and corrosion resistance

process:


drum technology

materials:

non-ferrous metals

coating system:

copper/nickel/tin



Anodising

performance:

fabrication of corrosion resistant, decorative oxide films

process:

anodic oxidation in fully automated equipment


materials:

aluminium and aluminium alloys

max. component size: 1500 x 2000 x 450 mm

colour:

natural aluminium or black



Degreasing

performance:

degreasing of oily or greasy metallic surfaces

process:

steam degreasing using chlorinated hydro-carbons in hermetically sealed equipment

material:

aluminium and aluminium alloys

min. component size:

30 x 30 x 30 mm

max. component size:

600 x 400 x 380 mm

max. component weight: 80 kg




OBERFLÄCHEN- VEREDELUNG GMBH

High quality surface treatment for electronic components



Transparent passivating (surface free from chromium)

characteristics: environmental compatibility due to chrome free passivation of the aluminium surfaces
process: fabrication of conversion coatings by immersion process
materials: aluminium und aluminium alloys
max. component size: 1500 x 2000 x 450 mm
colour: natural aluminium



Vibratory grinding (trowalization)

characteristics: deburring, removing of sharp edges, rough and fine grinding
process: treatment using vibration technique and grinding tools (trowalization)
materials: aluminium
max. component size: 230 x 200 mm



Anodisation facility

- economization of water by using spray-rinsing, automatized ion exchange installation, cascade water guided system and recirculation of splash water
- reduction of electrical energy by means of current density regulation
- reduction of chemicals by recirculation of the dragged-off chemicals using a compensation of the evaporation losses
- recycling of the sulphuric acid out of the anodizing bathes

Certificate

Standard **ISO 9001:2015**

Certificate Registr. No. **01 100 052055**

Certificate Holder:



**Fischer Oberflächen-
veredelung GmbH**
Nottebohmstr. 26
58511 Lüdenscheid
Germany

Scope:

Surfaces for electronics: goldplating, tinplating, nickelplating, anodizing, passivating, deburring

Proof has been furnished by means of an audit that the requirements of ISO 9001:2015 are met.

Validity:

The certificate is valid from 2017-12-15 until 2020-12-14.
First certification 2005

2017-12-15

TÜV Rheinland Cert GmbH
Am Grauen Stein · 51105 Köln

www.tuv.com



Terms and conditions of business

1. General provisions

1.1. The present General Terms and Conditions (GTC) apply to all of our business relationships with our customers ("Purchaser"). The GTC only apply if the Purchaser is an entrepreneur (§ 14 of the German Civil Code), a legal entity of public law or a special fund under public law.

The GTC particularly apply for contracts about the sale and/or the delivery of transportable objects ("Goods"), regardless of whether we manufacture the Goods ourselves or buy them in from suppliers (§§ 433, 651 of the German Civil Code). Unless otherwise agreed, the GTC apply, in the version valid at the time of the Purchaser's order or in the version last transmitted to them, as a framework agreement for similar future contracts, without us having to refer to them each time.

1.2. Our GTC apply exclusively. Deviating, contradicting or additional General Terms and Conditions of the Purchaser are only part of the contract if we have expressly authorised their validity. This approval requirement applies in any case, also if we make deliveries to the Purchaser without reserve, in full knowledge of their Terms and Conditions. Individual, isolated agreements with the Purchaser (including ancillary agreements, additions and changes) always take priority over these GTC. The content of this type of agreement, subject to counter-evidence, is to be determined according to a written contract or our written confirmation.

1.3. Legally relevant declarations and announcements of the Purchaser with regards to the contract (for example deadline agreements, defect notifications, withdrawal or reduction) are to be submitted in writing, i.e. in written or text form (for example letter, e-mail, fax). Legal form provisions and other certificates, especially in case of doubts about the legitimacy of the declaring party, remain unaffected.

1.4. References to the validity of legal provisions are only for clarification purposes. The legal provisions therefore apply even if there is no reference, unless they have been modified directly in these GTC or expressly excluded.

2. Quotations and orders

Our quotations shall be subject to change without notice and are non-binding. This applies also to information contained in price lists, leaflets etc. Delivery dates stated in our quotations or given to the purchaser by any other means are approximate, and we shall endeavour to keep to them. Delays in delivery shall give no right to claims, unless we have explicitly confirmed such delivery dates and an adequate period of grace granted to us has expired. Orders shall only be binding on us when they have been explicitly confirmed in writing, regardless of the form in which they have been placed with us. Statements made in catalogues are simply descriptions of goods and under no circumstances do they constitute warranted qualities. Furthermore, the characteristics of our samples cannot be regarded as warranted characteristics.

3. Prices

Prices shall be valid only when confirmed by us in writing. They are exclusive of VAT at the current rate and incidentals such as postage and packing, freight, insurance etc., as of storage. If delivery is made more than 4 months after the date of order, we shall be entitled to invoice the price valid at the date of despatch, even though different prices were initially confirmed. The price valid at the date of despatch shall also apply if the order was confirmed without prices being stated. When an order on call is placed, partial deliveries shall be invoiced at the price valid at the date of despatch. Any request by the purchaser for subsequent modifications shall entitle us to amend prices.

4. Conditions of payment

The invoiced sum is to be paid net within 30 days of date of invoice and delivery. If the purchaser is in default with any payment, we are entitled to claim interest for such default at the normal rate of interest charged for current accounts. If we are able to prove that we have incurred greater losses as a result of the delay, we shall be entitled to claim compensation for such damages. We are however entitled at any time, in the context of an ongoing business relationship, to execute a delivery in full or in part only against an advance deposit. We shall declare a corresponding reserve at the latest at the confirmation of the contract.

5. Set-off, right to retention

Only claims which have been recognised by us or have become legally binding may be offset against our invoices. Any right to a retention to be exercised

by the purchaser in connection with our claims is explicitly excluded. In case of defects in the delivery, the rights of the Purchaser remain unaffected, particularly with regards to point 10.3 of these GTC.

6. Delivery

The delivery is performed from the storage, wherever the place of fulfilment for the delivery and any subsequent fulfilment may be. Upon request by the Purchaser, the Goods will be sent to a different place of their choice (shipped purchase). Delivery of our goods is explicitly made on behalf of and at the risk of the purchaser. The risk shall pass over to the purchaser when the ordered goods leave our premises. The same applies if goods are collected in our premises from the point in time at which we notify the purchaser that they are ready for collection. Unless we have received instructions to the contrary from the purchaser, we shall decide at our discretion on the most economical delivery method without assuming any liability for the chosen means of delivery.

7. Specially manufactured goods

Components made according to a sample or a drawing or by special request must be taken over and paid for, unless they have a defect we are answerable for and which makes the components completely unfit for the purchaser's purposes. If their fitness for the purchaser's purposes is only reduced, the purchaser may request a reduction of payment but the contract shall not be cancelled.

8. Quantities

We are entitled to supply quantities which are above or below the ordered quantities by up to 10%. Such deviations are usual in this trade and the deliveries are deemed as being in compliance with the contract. If delivery quantities fall below the ordered quantities there shall be no right to subsequent delivery of the missing quantity.

9. Reservation of proprietary rights

9.1. All goods supplied shall remain our property until all current and future claims resulting from the Purchase contract and the business relationship with the purchaser (secured claims) have been paid in full. The purchaser is entitled to dispose of the purchased goods in the ordinary course of business transactions. Reservation of proprietary rights also applies to products resulting from processing, mixing up or combining our goods, in which case we are considered as manufacturers. In the case where our goods are processed, mixed up or combined with goods of third parties, and the proprietary rights of such third parties remain in force, we are entitled to co-ownership according to the proportion of the amount invoiced for such processed goods. In such cases such rights to co-ownership shall be safeguarded by the purchaser.

9.2. The purchaser shall transfer to us, as a security, his claims against third parties resulting from the resale of our goods in full or in the proportion of our co-ownership (see subparagraph 9.1). He is entitled to collect the amount of such claims on our behalf until revoked or until cessation of his payments made to us. The purchaser is not entitled to assign these claims to third parties.

9.3. The purchaser is not entitled to mortgage or transfer the goods which are subject to reservation by way of security.

9.4. The purchaser shall advise us immediately at any seizure of our goods or of any infringement of our rights by third parties.

9.5. In case of a default in payment or a deterioration in the financial situation, we are entitled to request immediate handing over of the goods which are subject to reservation. Any time limited claims shall immediately become due.

9.6. If the value of the securities exceeds our claims by more than 20%, securities to a corresponding amount will be released by us on request at our discretion.

10. Warranty

10.1. We expressly point out that all information and data is given to the best of our knowledge and belief. The user is solely responsible for the proper use of our products and he should check their suitability for the intended application.

Fischer Elektronik do not assume any warranty, whether expressed or implied, for the suitability, function or merchantability of their products in specific or general applications, and they cannot be held liable for accidental or consequential damage due to non-observance of the above.

10.2. Claims for defects can only be considered if the purchaser has complied with their obligation to check goods and submit a complaint as per Sections

377, 381 of the German Commercial Code [HGB]. If goods have a defect attributable to us, we are obliged to effect a cure, excluding the purchaser's right to withdraw from the contract or to reduce the purchase price (reduction), unless we are entitled to refuse to effect a cure by virtue of legal regulations. The purchaser shall grant us an adequate period of grace for effecting a cure. A cure may at our discretion be an elimination of the defect (rectification) or the supply of new products. We are entitled to determine the cure owed according to the payment of the purchase price due by the Purchaser. The Purchaser, however, is entitled to retain a part of the purchase price that is proportionate to the defect. The expenses incurred for the verification and cure, particularly transport, road, work and materials costs (not: expansion and installation costs) are borne by us, if there is indeed a defect. Otherwise, we can require that the Purchaser bear the costs arising from the unjustified defect rectification request (particularly examination and transport costs), unless the Purchaser could not have been aware that the defect rectification was unnecessary.

10.3. If goods have a defect attributable to us, we are obliged to provide subsequent fulfilment, excluding the purchaser's right to withdraw from the contract or to reduce the purchase price (abatement), unless we are entitled to refuse subsequent fulfilment by virtue of legal provisions. The purchaser shall grant us an adequate period of grace for subsequent fulfilment. Subsequent fulfilment may at our discretion be an elimination of the defect (rectification) or the supply of new products.

10.4. If rectification of the defect has failed, the purchaser shall be entitled to request a reduction in the purchase price (abatement) or to withdraw from the contract. Rectification shall be deemed to have failed after the second vain attempt, unless further attempts are reasonable in view of the object of the contract and can be reasonably imposed on the purchaser.

10.5. The purchaser's right to put forward further claims for damages shall remain unaffected by this.

10.6. If it becomes apparent (by the opening of an application for an insolvency procedure for example) after the conclusion of the contract that our claims to the purchase price are endangered due to lacking payment capacities of the Purchaser, we will then be entitled to refuse the delivery and – after a possible period of notice – to withdraw from the contract in accordance with the legal provisions (§ 321 of the German Civil Code). For contracts about the manufacturing of specific items (making to specification), we can declare the withdrawal immediately; the legal regulations about the dispensability of giving a period of notice remain unaffected.

11. Withdrawal

When delivery in accordance with the contract is not possible for reasons beyond our control, we are entitled to withdraw from the contract. Such withdrawal shall not entitle the purchaser to assert any right against us.

12. Export clause

We are not obliged to reimburse damages arising from delays in delivery or it being completely impossible to deliver as a result of statutory or official export restrictions, unless we act with intent or gross negligence suffered by the Customer or other persons. The Customer's duty to pay the agreed remuneration shall not be affected by disruptions in our performance as a result of export restrictions. We shall be entitled to withdraw from the contract if, after the contract is signed, our performance is disrupted as a result of export restrictions.

13. Place of performance and jurisdiction, applicable law

13.1. The place of performance and the place of venue for deliveries and payments and/or any litigation arising between us and the purchaser shall be the headquarters of our company.

13.2. The relationship between the contractual parties shall be regulated solely in accordance with the law in force in the Federal Republic of Germany. The regulations of international uniform law, particularly the UN CISG, shall not apply.

Status as at: 29.07.2019

The latest T&Cs shall apply at all times. They may be downloaded at www.fischer elektronik.de

art. no.	HEATSINKS SURFACES & CASES SURFACES	
AL		raw degreased aluminium
BZ		raw pickled aluminium
LP		outside black lacquered RAL 9005/transparent passivated
ME		clear anodised
MI		solderable surface
SA		black anodised
TP		chrome-free transparent passivated

art. no.	CONNECTOR CONTACT SURFACE FINISH	
G		gold-plated
S		selective gold-plated
Z		tin-plated

art. no.	RAL	COLOURS	ARTICLES
GO	6026	 opal green	system cases "RackCase"/shell cases
NB	5022	 night blue	system cases "RackCase"/shell cases
S	9005	 deep black	TG/shell cases/system cases "RackCase"
TB	5018	 turquoise blue	system cases "RackCase"/shell cases
UL	5002	 ultramarine blue	Plusline/shell cases



Extruded heatsinks,
LED-heatsinks,
Cooling aggregates,
Thermally conductive mat.



Cases,
19" technology,
Test equipment



Slip-case
for collecting
the catalogues

Fischer Elektronik GmbH & Co. KG

Nottebohmstraße 28 • 58511 Lüdenscheid
GERMANY

Fon +49 2351 435-0

Fax +49 2351 45754

E-mail info@fischerelektronik.de

Website www.fischerelektronik.de

Find us on
Facebook

