



Si720x Switch/Latch Hall Effect Magnetic Position Sensor Data Sheet

The Si7201/2/3/4/5/6 family of Hall effect magnetic sensors and latches from Silicon Labs combines a chopper-stabilized Hall element with a low-noise analog amplifier, 13-bit analog-to-digital converter, and flexible comparator circuit. Leveraging Silicon Labs' proven CMOS design techniques, the Si720x family incorporates digital signal processing to provide precise compensation for temperature and offset drift.

Compared with existing Hall effect sensors, the Si720x family offers industry-leading sensitivity, which enables use with larger air gaps and smaller magnets. For battery-powered applications, the Si720x family offers very low power consumption to improve operating life. For automotive applications, the Si720x family is AEC-Q100 qualified.

The Si720x devices are offered in 3-pin SOT23 and TO-92 packages, with power, ground, and a single output pin that goes high or low as the magnetic field increases. With the three-pin package, tamper indication is by the pin going back to its zero field level at high magnetic field.

In the 5-pin SOT23 and 8-pin DFN packages, pins are available for both sleep mode activation and separate tamper indication.

Applications:

- Replacement of reed switches in consumer, automotive, and security applications
- Automotive position sensing of HVAC valve, head rest, seat track, side mirrors, sunroof, door locks, and other mechanical devices
- BLDC motor control
- Camera image stabilization, zoom, and autofocus
- Fluid level sensing - Control knobs and selector switches
- General-purpose mechanical position sensing

FEATURES

- High-Sensitivity Hall Effect Sensor
 - Maximum B_{OP} operating point/minimum field strength of <1.1 mT
 - Omnipolar or unipolar operation
 - Integrated digital signal processing for temperature and offset drift compensation
- Low 400 nA Typical Current Consumption
- Selectable / Programmable Sensitivity, Hysteresis, Output Polarity and Sample Rate
- Sensitivity Drift $< \pm 3\%$ over Temperature
- Wide Power Supply Voltage
 - 1.7 to 5.5 V
 - 3.3 to 26.5 V
- AEC-Q100 Qualified for Automotive Applications
- Selectable Output Options
 - Open-drain output
 - Digital high/low output
 - 2-wire current source
- Industry-Standard Packaging
 - Surface mount SOT-23 (3 or 5 pin)
 - Through hole TO-92 (3-pin)
 - 1.4 x 1.6 mm 8-pin DFN package (coming soon)




Table of Contents

1. Electrical Specifications	3
2. Functional Description	8
3. DISABLE Pin Timing	.10
4. Pin Description	.11
5. Ordering Guide	.13
6. Package Outline	17
6.1 SOT23 3-Pin Package	.17
6.2 SOT23 5-Pin Package	.18
7. Land Patterns	20
7.1 SOT23 Three-Pin PCB Land Pattern	.20
7.2 SOT23 Five-Pin PCB Land Pattern	.21
8. Top Marking	22
8.1 SOT23 3-Pin Topmarking	.22
8.2 SOT23 5-Pin Topmarking	.22

1. Electrical Specifications

Unless otherwise specified, all min/max specifications apply over the recommended operating conditions.

Table 1.1. Recommended Operating Conditions

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Power Supply	V _{DD}	Si7201/2/3/4	1.71		5.5 ¹	V
Power Supply	V _{DD}	Si7205/6	3.3		26.5	V
Temperature	T _A	I grade	-40		+125 ²	°C

Note:

1. 3.6 V for sensitive parts (see ordering guide).
2. 0-70°C for sensitive parts (F grade) (see ordering guide).

Table 1.2. General Specifications¹

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Input voltage high	V _{IH}	DIS pin	0.7 x V _{DD}	-	-	V
Input Voltage Low	V _{IL}	DIS pin	-	-	0.3 x V _{DD}	V
Input voltage range	V _{IN}	DIS pin	0		V _{DD}	V
Input Leakage	I _{IL}	DIS pin			1	µA
Output voltage low	V _{OL}	TAMPERb pin I _{OL} = 3 mA V _{DD} > 2 V			0.4	V
		TAMPERb pin I _{OL} = 2 mA V _{DD} > 1.7 V			0.2	V
		TAMPERb pin I _{OL} = 6 mA V _{DD} > 2 V			0.6	V
Output voltage high	V _{OH}	TAMPERb pin I _{OH} = 2 mA V _{DD} > 2.25 V	V _{DD} - 0.4			V
Current Consumption	I _{DD}	Conversion in progress: V _{DD} = 1.8 V		3.9		mA
		V _{DD} = 3.3 V		5.2		
		V _{DD} = 5 V		6.6		
		Sleep Mode		100		nA
		Idle mode		360		µA
		Sleep timer enabled average at V _{DD} = 3.3 V and 200 msec sleep time		0.4		µA

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Conversion time	T _{CONV}	First conversion when waking from sleep or idle		11		μS
		Additional conversions in a burst		8.8		μS
Sleep time ²	T _{SLEEP}	Factory configurable from 1 to 200 msec ±20%				
Idle time ³	T _{IDLE}	Minimum	11.9	13.2	14.5	usec
		Maximum	185	206	227	msec
Wake up time	T _{WAKE}	Time from V _{DD} > 1.7 V to first measurement			2	msec

Note:

1. TAMPERb and DIS pin specifications apply when the pin is present. These functions are only supported for the V_{DD} range of 1.7 – 5.5V (Si7203/4).
2. Parts go to sleep or idle mode between measurements. Sleep time can factory programmed from 0.875 msec to 254 msec nominal with accuracy of ±30%. Typically sleep time is set to 100 msec and the sleep time counter is adjusted to give accuracy within ±10%.
3. Idle time can be factory programmed from 13.2 μsec to 206 msec ±10% or set to zero in which case conversions are done every 8.8 μsec. Normally idle time is only used at higher sample speeds.

Table 1.3. Output Pin Specifications

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Si7201/2/3/4						
Output voltage low Open drain or push pull	V _{OL}	I _{OL} = 3 mA V _{DD} > 2 V			0.4	V
		I _{OL} = 2 mA V _{DD} > 1.7 V			0.2	V
		I _{OL} = 6 mA V _{DD} > 2 V			0.6	V
Leakage Output high Output pin open drain	I _{OH}				1	μA
Output voltage high Output pin push pull	V _{OH}	I _{OH} = 2 mA V _{DD} > 2.25 V	V _{DD} - 0.4			V
Slew rate	T _{SLEW}			5		%V _{DD} /nS
Si7205/6						
Output voltage low	V _{OL}	I _{OL} = 11.4 mA V _{DD} > 6 V			0.4	V

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Safe continuous sink current					20	mA
Leakage Output high Output pin open drain	I_{OH}				1	μA
Slew rate Digital output mode	T_{SLEW}			5		$\%V_{DD}/nS$
Output pin shorted to VDD	I_{SHORT}	$V_{DD} = 12 V$ Average current as pin cycles		4		mA

The Si7205 and Si7206 can be configured to signal the status equivalent to output high or low by modulating the power supply current. If configured in this way following are the specifications for the amount of current that will be drawn for the “output high” state.

Table 1.4. I_{DD} Signaling

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
I_{DD} signaling current	I_{DO}	$V_{DDH} > 6 V$	8	10	12	mA

Table 1.5. Magnetic Sensor²

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Offset ¹	B_{OFF}	20 mT scale $V_{DD} = 1.71$ to $3.6 V$ 0-70°C		± 150	± 250	μT
		20 mT scale $V_{DD} = 1.71$ to $5.5 V$ Full temperature range		± 250	± 400	μT
Gain accuracy		0-70°C			5	%
		Full temperature range			8	%
RMS Noise ³		room Temp, 20 mT range, $V_{DD} = 5 V$		30		μT rms

Note:

1. See the Ordering Guide to determine Bop/Brp for various OPNs.
2. See ordering guide for operating a release points. These are defined as maximum operating point and minimum release point -40°C to +150°C and do not include the effect of noise.
3. For a single conversion. This can be reduced by the square root of N by filtering over N samples. See ordering guide for samples taken per measurement.

Table 1.6. Temperature Compensation

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Bop and Brp vs temperature		No compensation 0-70°C		< ±0.05		%/°C
		Neodymium compensation		-0.12		%/°C
		Ceramic compensation		-0.2		%/°C

Table 1.7. Thermal Characteristics

Parameter	Symbol	Test Condition	Value	Unit
Junction to air thermal resistance	θ_{JA}	JEDEC 4 layer board no airflow SOT23-5	212.8	°C/W
Junction to board thermal resistance	θ_{JB}	JEDEC 4 layer board no airflow SOT23-5	45	°C/W
Junction to air thermal resistance	θ_{JA}	JEDEC 4 layer board no airflow SOT23-3	254.6	°C/W
Junction to board thermal resistance	θ_{JB}	JEDEC 4 layer board no airflow SOT23-3	54.8	°C/W

Table 1.8. Absolute Maximum Ratings¹

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Ambient temperature under bias			-55		125	°C
Storage temperature			-65		150	°C
Si7201/2/3/4						
Voltage on I/O pins			-0.3		$V_{DD}+0.3$	V
Voltage on V_{DD} with respect to ground			-0.3		6	V
ESD tolerance		HBM			2	kV
		CDM			1.25	kV
Si7205/6						
Voltage on output pin ²			-21		40	V
Voltage on V_{DD} with respect to ground ³			-21		40	V
ESD tolerance		HBM			8	kV
		CDM			1.25	kV

Note:

1. Absolute maximum ratings are stress ratings only, operation at or beyond these conditions is not implied and may shorten the life of the device or alter its performance.
2. The output pin can withstand EMC transients per ISO 7637-2-2-11 and Ford EMC-CS-2009.1 with a current limiting resistor of [TBD] ohms.
3. V_{DD} can withstand automotive EMC transients per ISO 7637-2-2-11 and Ford EMC-CS-2009.1 with a current limiting resistor of [TBD] ohms.

2. Functional Description

The Si7201/2/3/4/5/6 family of Hall Effect magnetic sensors digitize the component of the magnetic field in the z axis of the device (positive field is defined as pointing into the device from the bottom). The digitized field is compared to a pre-programmed threshold and the output pin goes high or low if the threshold is crossed. The parts are normally used to detect the presence or absence of a magnet in security systems, as position sensors or for counting revolutions.

Table 2.1. Part Ordering Guide

Part Number	Description
Si7201	Low voltage switches
Si7202	Low voltage latches
Si7203	Low Voltage switch with tamper and/or disable pins
Si7204	Low voltage latches with tamper and/or disable pins
Si7205	High Voltage switches
Si7206	High Voltage latches

The output pin (push pull or open collector) can go high or low when the magnetic field crosses a threshold. The output pin configuration is determined by the type of part ordered.

The parts are preconfigured for the magnetic field measurement range, magnetic field operate and release points, sleep time, temperature compensation, tamper threshold and digital filtering and will wake into this mode when first powered. The specific configuration output type (open collector or push pull) are determined by the part number.

Following is a list of configuration options:

- **Measurement Range:** This is normally set so that after temperature compensation the full scale output is ± 20.47 mT or ± 204.7 mT. For convenience these are referred to as the 20 mT and 200 mT scales
- **Decision Points:**
 - For 20 mT switch mode parts, the middle of the decision point can be configured from 0.08 mT to 19.2 mT. For 200 mT parts, the middle point of the decision threshold can be programmed from 0.8 mT to 192 mT
 - For latch mode parts the middle of the decision point is zero.
 - For 20 mT scale switch mode parts, the hysteresis can be programmed to ± 0.04 mT to ± 8.96 mT. On the 200 mT scale, these numbers are multiplied by 10.
 - For latch mode parts the decision points can be configured from ± 0.08 mT to ± 17.92 mT on the 20 mT scale. On the 200 mT scale these numbers are multiplied by 10.
 - For 20 mT scale parts, the tamper threshold can be configured from 2.65 mT to 19.84 mT. On the 200 mT scale these numbers are multiplied by 10. Tamper detection can also be disabled.
- **Digital Filtering:** To reduce noise in the output (normally 0.03 mT RMS on the 20 mT scale), digital filtering can be applied. The digital filtering can be done to a burst a measurements (FIR filter) or can be configured to average measurements in IIR style. The filtering can be done over a number of samples in powers of 2 (1,2,4,8,...) for up to 2^{12} (4096) samples
- **Time between Measurements (or Measurement Bursts for the Case of FIR Filtering):**
 - For lowest power, the part can be configured to sleep between measurements. Sleep times are configurable from 1 msec to 200 msec.
 - For faster measurement rates and for analog output mode the part is configured to idle between samples. Idle times are variable from 13.2 μ sec to 206 msec nominally.
- **The Digital Output Pin:**
 - The direction in which the output pin goes in response to an increase in field
 - There is an option to take the magnitude of the field prior to the comparison so that the polarity is not field dependent
 - For 3 pin parts in the case of tamper detection the output pin will go to its zero field value (which in security systems is normally an indication of door or window open).
 - For 4 and 5 pin parts there is a separate tamper indication pin
- **Temperature compensation of the magnetic field response to compensate for the nominal drop in magnetic field output of common magnets with increasing temperature.**

Note: In this case accuracy is defined at 25°C and the sensitivity increases at higher temperature

Examples:




Figure 2.1. Unipolar Switch with Tamper




Figure 2.2. Omnipolar Switch with Tamper




Figure 2.3. Latch

3. DISABLE Pin Timing

For a part that has a DISABLE pin, DISABLE high will put the part in complete sleep mode with I_{DD} typical of 100 nA. When DISABLE goes low, the part will wake and initiate a measurement. For a single measurement, this takes 11 μ sec typically. Additional measurements in a burst take 8.8 μ sec. Once the measurement (burst) is complete, the output pin status is updated and the part enters idle mode. The part will make a new measurement or measurement burst at the time-interval determined by the idle timer (typically 1 msec). The idle timer is reset when DISABLE transitions from high to low, so the time from the first measurement until the next measurement will always be the programmed idle time.

The DISABLE pin should be kept low for at least one measurement cycle. For example, for a part that only does a single measurement, a measurement will complete in 11 μ sec $\pm 10\%$, so keep disable low for 12.1 μ sec plus margin, so typically 15 μ sec.

When disable returns high, a measurement in progress (if any) will complete and the part will enter sleep mode.

As the idle time is typically long (i.e. 1 msec) compared to the measurement time (i.e. 11 μ sec), it is possible to keep the DISABLE pin low duration short (i.e. 15 μ sec) and have a long period in the sleep state. This is an effective way to control the sample rate and power.

For example, if the part is programmed to make a single measurement at a time and is programmed with an idle time of 1 msec and DISABLE is pulsed low for 15 μ sec every 100 msec, then the average I_{DD} will be:

- 11 μ sec to wake and make a measurement at I_{DD} typical of 5.2 mA (3.3V)/(50.015 msec cycle time) = 1.14 μ A
- 4 μ sec in idle mode at typical current of 360 μ A/(50.015 msec cycle time) = 0.03 μ A
- 50 msec in sleep mode at 100 nA/(50.015 msec cycle time) = 0.099uA
- Or 1.27 μ A total

As the programmed idle time is shorter than the DISABLE low time in the example, the value of the programmed idle time does not make a difference.

4. Pin Description




Figure 4.1. Si720xxx Pin Assignments

Note:

The 3-pin option includes part numbers: Si7201/2/5/6.

The SOT-23 5 pin and DFN 8 pin options include part numbers: Si7203/4.

Table 4.1. Si7201/2/5/6 (3-pin)

Pin Name	Pin Number	Description
VDD	1	Power +1.7 to +5.5 V or 3.3 to 26.5 V
OUT1	2	Switch/latch output
GND	3	Ground

Table 4.2. Si7203/4/5 (5-pin)

Pin Name	Pin Number	Description
OUT2/TAMPERb	1	OUT2/TAMPERb (tamper/high field indicator)
GND	2	Ground
DIS	3	Disables part (puts into sleep mode) when high. Measurement cycle will resume when pin goes low
VDD	4	Power +1.7 to +5.5 V
OUT1	5	Switch/latch output

Table 4.3. Si7203/4 (DFN 8-pin package)

Pin Name	Pin Number	Description
VDD	8	Power +1.7 to +5.5 V
GND	1, 5	Ground
OUT1	6	Switch/latch output
DISb 2 Disable (puts part in lowest power mode with no sampling)	4	OUT2/TAMPERb (tamper/high field indicator)

Table 4.4. Si7201/2/5/6 TO-92

Pin Name	Pin Number	Description
VDD	1	Power
GND	2	Ground
OUT1	3	Output

5. Ordering Guide

Part Number ¹	Output Type	Output Polarity (high field)	IDD (typ. @3.3V)	BOP, BRP ²	Sleep/ Idle Time	Temperature Compensation	Tamper Threshold (typ.)	Digital Filtering	VDD	Package	Temperature Rating
Si7201-B-00-FV(R)	Omnipolar Switch	Low (push-pull)	0.4 μ A	BOP = ± 1.1 mT (max) BRP = ± 0.2 mT (min) BOP - BRP = 0.4 mT (typ)	200 msec (sleep)	None	None	None	1.7 - 3.6 V	SOT23-3	0°C - 70°C
Si7201-B-01-FV(R)	Omnipolar Switch	Low (push-pull)	0.4 μ A	BOP = ± 1.1 mT (max) BRP = ± 0.2 mT (min) BOP - BRP = 0.4 mT (typ)	200 msec (sleep)	None	± 19.8 mT	None	1.7 - 3.6 V	SOT23-3	0°C - 70°C
Si7201-B-02-FV(R)	Omnipolar Switch	High (push-pull)	1.1 μ A	BOP = ± 0.9 mT (max) BRP = ± 0.2 mT (min) BOP - BRP = 0.2 mT (typ)	200 msec (sleep)	0.12%/°C	± 19.8 mT	4 sample FIR	1.7 - 3.6 V	SOT23-3	0°C - 70°C
Si7201-B-03-IV(R)	Omnipolar Switch	High (push-pull)	57 μ A	BOP = ± 2.8 mT (max) BRP = ± 1.1 mT (min) BOP - BRP = 0.6 mT (typ)	1 msec (sleep)	None	None	None	1.7 - 3.6 V	SOT23-3	-40°C - 125°C
Si7201-B-04-IV(R)	Omnipolar Switch	Low (push-pull)	0.4 μ A	BOP = ± 1.4 mT (max) BRP = ± 0.2 mT (min) BOP - BRP = 0.4 mT (typ)	200 msec (sleep)	None	None	None	1.7 - 5.5 V	SOT23-3	-40°C - 125°C

Part Number ¹	Output Type	Output Polarity (high field)	IDD (typ. @3.3V)	BOP, BRP ²	Sleep/ Idle Time	Temperature Compensation	Tamper Threshold (typ.)	Digital Filtering	VDD	Package	Temperature Rating
Si7201-B-05-IV(R)	Omnipolar Switch	Low (push-pull)	0.4 μ A	BOP = ± 2.0 mT (max) BRP = ± 0.6 mT (min) BOP - BRP = 0.6 mT (typ)	200 msec (sleep)	None	± 19.8 mT	None	1.7 - 5.5 V	SOT23-3	-40°C - 125°C
Si7201-B-06-IV(R)	Omnipolar Switch	Low (open drain)	0.4 μ A	BOP = ± 2.0 mT (max) BRP = ± 0.6 mT (min) BOP - BRP = 0.6 mT (typ)	200 msec (sleep)	None	None	None	1.7 - 5.5 V	SOT23-3	-40°C - 125°C
Si7201-B-07-IV(R)	Omnipolar Switch	Low (open drain)	0.4 μ A	BOP = ± 2.0 mT (max) BRP = ± 0.6 mT (min) BOP - BRP = 0.6 mT (typ)	200 msec (sleep)	None	± 19.8 mT	None	1.7 - 5.5 V	SOT23-3	-40°C - 125°C
Si7201-B-08-IV(R)	Omnipolar Switch	Low (push-pull)	0.4 μ A	BOP = ± 3.4 mT (max) BRP = ± 1.6 mT (min) BOP - BRP = 0.6 mT (typ)	200 msec (sleep)	0.12%/°C	None	None	1.7 - 5.5 V	SOT23-3	-40°C - 125°C
Si7202-B-00-FV(R)	Latch	High (push-pull)	0.4 μ A	BOP(max) = +0.65mT BOP(min) = +0.15 mT BRP(min) = -0.65 mT BRP(max) = -0.15 mT BOP - BRP = 0.8 mT (typ)	200 msec (sleep)	None	None	None	1.7 - 3.6 V	SOT23-3	0°C - 70°C

Part Number ¹	Output Type	Output Polarity (high field)	IDD (typ. @3.3V)	BOP, BRP ²	Sleep/ Idle Time	Temperature Compensation	Tamper Threshold (typ.)	Digital Filtering	VDD	Package	Temperature Rating
Si7202-B-01-IV(R)	Latch	Low (push-pull)	0.4 μ A	BOP(max) = +1.4 mT BOP(min) = +0.6 mT BRP(min) = -1.4 mT BRP(max) = -0.6 mT BOP - BRP = 2.0 mT (typ)	200 msec (sleep)	None	None	None	1.7 - 5.5 V	SOT23-3	-40°C - 125°C
Si7203-B-00-FV(R)	Omnipolar Switch	High (open drain)	0.4 mA (typ) 0.1 μ A (DIS high)	BOP = \pm 1.1 mT (max) BRP = \pm 0.2 mT (min) BOP - BRP = 0.4 mT (typ)	1 msec (idle)	None	\pm 19.8 mT	None	1.7 - 3.6 V	SOT23-5	0°C - 70°C
Si7204-B-00-FV(R)	Latch	High (push-pull)	0.4 mA (typ) 0.1 μ A (DIS high)	BOP(max) = +1.1 mT BOP(min) = +0.6 mT BRP(min) = -1.1 mT BRP(max) = -0.6 mT BOP - BRP = 1.8 mT (typ)	1 msec (idle)	None	None	None	1.7 - 3.6 V	SOT23-5	0°C - 70°C
Si7205-B-00-IV(R)	Omnipolar Switch	Low (open drain)	5 μ A	BOP = \pm 3.0 mT (max) BRP = \pm 0.8 mT (min) BOP - BRP = 0.6 mT (typ)	10 msec (sleep)	None	None	None	3.3 - 26.5 V	SOT23-3	-40°C - 125°C





Part Number ¹	Output Type	Output Polarity (high field)	IDD (typ. @3.3V)	BOP, BRP ²	Sleep/ Idle Time	Temperature Compensation	Tamper Threshold (typ.)	Digital Filtering	VDD	Package	Temperature Rating
Si7206-B-00-IV(R)	Latch	Low (open drain)	5 μ A	BOP(max) = +1.4 mT BOP(min) = +0.6 mT BRP(min) = -1.4 mT BRP(max) = -0.6 mT BOP - BRP = 2.0 mT (typ)	10 msec (sleep)	None	None	None	3.3 - 26.5 V	SOT23-3	-40°C - 125°C

Note:

1. A is the die revision. The next two digits are used with this look up table to give more specific information. I or F is the temperature range -40 to +125°C or 0 to 70°C. E is the temperature range (-40 to +150°C). B, M, or V is the package type (TO92, DFN8, or SOT23) the optional (R) is the designator for tape and reel (Find out number from OPS). Parts not ordered by the full reel will be supplied in cut tape.
2. Specified at 25°C for parts with temperature compensation. Scale is 20 mT if Bop/Brp and Tamper threshold support this, otherwise it is 200 mT.
3. North pole of a magnet at the bottom of a SOT23 package is defined as positive field.

6. Package Outline

6.1 SOT23 3-Pin Package




Dimension	MIN	MAX
A	--	1.25
A1	0.00	0.10
A2	0.85	1.15
b	0.30	0.50
c	0.10	0.20
D	2.90 BSC	
E	2.80 BSC	
E1	1.60 BSC	
e	0.95 BSC	
e1	1.90 BSC	
L	0.30	0.60
L2	0.25 BSC	
θ	0°	8°
aaa	0.15	
bbb	0.15	
ccc	0.10	
ddd	0.20	

Note:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.
2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.
3. This drawing conforms to the JEDEC Solid State Outline MO-193, Variation AB.
4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020D specification for Small Body Components.

6.2 SOT23 5-Pin Package




Dimension	MIN	MAX
A	--	1.10
A1	0.025	0.10
A2	0.85	0.90
b	0.30	0.45
c	0.10	0.20
D	2.90 BSC	
E	2.75 BSC	
E1	1.60 BSC	
e	0.95 BSC	
e1	1.90 BSC	
L	0.30	0.50
L2	0.25 BSC	
θ	0°	8°
aaa	0.15	
bbb	0.15	
ccc	0.10	
ddd	0.20	

Note:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.
2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.
3. This drawing conforms to the JEDEC Solid State Outline MO-193, Variation AB.
4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020D specification for Small Body Components.


7. Land Patterns

7.1 SOT23 Three-Pin PCB Land Pattern



Dimension	(mm)
C	2.70
E	0.95
X	1.05
Y	0.60

7.2 SOT23 Five-Pin PCB Land Pattern



Dimension	(mm)
C	2.70
E	0.95
X	1.05
Y	0.60

Note:

General


1. All dimensions shown are in millimeters (mm) unless otherwise noted.
2. Dimensioning and Tolerancing is per the ANSI Y14.5M-1994 specification.
3. This Land Pattern Design is based on the IPC-7351 guidelines.
4. All dimensions shown are at Maximum Material Condition (MMC). Least Material Condition (LMC) is calculated based on a Fabrication Allowance of 0.05 mm.

Card Assembly


1. A No-Clean, Type-3 solder paste is recommended.
2. The recommended card reflow profile is per the JEDEC/IPC J-STD-020D specification for Small Body Components.


8. Top Marking

8.1 SOT23 3-Pin Topmarking



8.2 SOT23 5-Pin Topmarking






Smart.
Connected.
Energy-Friendly.



Products
www.silabs.com/products



Quality
www.silabs.com/quality



Support and Community
community.silabs.com

Disclaimer

Silicon Labs intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Labs products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Labs reserves the right to make changes without further notice and limitation to product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Silicon Labs shall have no liability for the consequences of use of the information supplied herein. This document does not imply or express copyright licenses granted hereunder to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any Life Support System without the specific written consent of Silicon Labs. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Labs products are not designed or authorized for military applications. Silicon Labs products shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons.

Trademark Information

Silicon Laboratories Inc.®, Silicon Laboratories®, Silicon Labs®, SiLabs® and the Silicon Labs logo®, Bluegiga®, Bluegiga Logo®, Clockbuilder®, CMEMS®, DSPLL®, EFM®, EFM32®, EFR®, Ember®, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Ember®, EZLink®, EZRadio®, EZRadioPRO®, Gecko®, ISOModem®, Micrium, Precision32®, ProSLIC®, Simplicity Studio®, SiPHY®, Telegesis, the Telegesis Logo®, USBXpress®, Zentri and others are trademarks or registered trademarks of Silicon Labs. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. All other products or brand names mentioned herein are trademarks of their respective holders.



Silicon Laboratories Inc.
400 West Cesar Chavez
Austin, TX 78701
USA

<http://www.silabs.com>