

# LC<sup>2</sup>MOS Quad 8-Bit D/A Converter

# AD7226


### FEATURES

Four 8-Bit DACs with Output Amplifiers Skinny 20-Lead DIP, SOIC, SSOP, and PLCC Packages Microprocessor-Compatible TTL/CMOS-Compatible No User Trims Extended Temperature Range Operation Single Supply Operation Possible

### **APPLICATIONS**

Process Control Automatic Test Equipment Automatic Calibration of Large System Parameters, e.g., Gain/Offset

### FUNCTIONAL BLOCK DIAGRAM



### **GENERAL DESCRIPTION**

The AD7226 contains four 8-bit voltage-output digital-toanalog converters, with output buffer amplifiers and interface logic on a single monolithic chip. No external trims are required to achieve full specified performance for the part.

Separate on-chip latches are provided for each of the four D/A converters. Data is transferred into one of these data latches through a common 8-bit TTL/CMOS (5 V) compatible input port. Control inputs A0 and A1 determine which DAC is loaded when  $\overline{WR}$  goes low. The control logic is speed-compatible with most 8-bit microprocessors.

Each D/A converter includes an output buffer amplifier capable of driving up to 5 mA of output current. The amplifiers' offsets are laser-trimmed during manufacture, thereby eliminating any requirement for offset nulling.

Specified performance is guaranteed for input reference voltages from 2 V to 12.5 V with dual supplies. The part is also specified for single supply operation at a reference of 10 V.

The AD7226 is fabricated in an all ion-implanted high speed Linear Compatible CMOS (LC<sup>2</sup>MOS) process, which has been specifically developed to allow high speed digital logic circuits and precision analog circuits to be integrated on the same chip.

### REV. C

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.

### **PRODUCT HIGHLIGHTS**

1. DAC-to-DAC Matching Since all four DACs are fabricated on the same chip at the same time, precise matching and tracking between the DACs is inherent.

- 2. Single-Supply Operation The voltage mode configuration of the DACs allows the AD7226 to be operated from a single power supply rail.
- 3. Microprocessor Compatibility

The AD7226 has a common 8-bit data bus with individual DAC latches, providing a versatile control architecture for simple interface to microprocessors. All latch enable signals are level triggered.

4. Small Size

Combining four DACs and four op amps plus interface logic into a 20-pin package allows a dramatic reduction in board space requirements and offers increased reliability in systems using multiple converters. Its pinout is aimed at optimizing board layout with all the analog inputs and outputs at one end of the package and all the digital inputs at the other.

# 

# **DUAL SUPPLY**

Parameter	K, B Versions <sup>2</sup>	Unit	Conditions/Comments
STATIC PERFORMANCE			
Resolution	8	Bits	
Total Unadjusted Error	±1	LSB max	$V_{DD} = 15 \text{ V} \pm 5\%, V_{REF} = 10 \text{ V}$
Relative Accuracy	$\pm 0.5$	LSB max	
Differential Nonlinearity	$\pm 1$	LSB max	Guaranteed Monotonic
Full-Scale Error	$\pm 0.5$	LSB max	
Full-Scale Temperature Coefficient	±20	ppm/°C typ	$V_{DD} = 14 \text{ V}$ to 16.5 V, $V_{REF} = +10 \text{ V}$
Zero Code Error	$\pm 20$	mV max	
Zero Code Error Temperature Coefficient	±50	µV/°C typ	
REFERENCE INPUT			
Voltage Range	2 to $(V_{DD} - 4)$	V min to V max	
Input Resistance	2	$k\Omega$ min	
Input Capacitance <sup>3</sup>	50	pF min	Occurs when each DAC is loaded with all 0s.
	200	pF max	Occurs when each DAC is loaded with all 1s.
DIGITAL INPUTS			
Input High Voltage, V <sub>INH</sub>	2.4	V min	
Input Low Voltage, V <sub>INL</sub>	0.8	V max	
Input Leakage Current	±1	µA max	$V_{IN} = 0 V \text{ or } V_{DD}$
Input Capacitance	8	pF max	
Input Coding	Binary	1	
DYNAMIC PERFORMANCE			
Voltage Output Slew Rate <sup>4</sup>	2.5	V/µs min	
Voltage Output Settling Time <sup>4</sup>	4	µs max	$V_{REF}$ = 10 V; Settling Time to ±1/2 LSB
Digital Crosstalk	10	nV secs typ	
Minimum Load Resistance	2	$k\Omega$ min	$V_{OUT} = 10 V$
POWER SUPPLIES			
V <sub>DD</sub> Range	11.4/16.5	V min/V max	For Specified Performance
I <sub>DD</sub>	13	mA max	Outputs Unloaded; $V_{IN} = V_{INL}$ or $V_{INH}$
I <sub>SS</sub>	11	mA max	Outputs Unloaded; $V_{IN} = V_{INL}$ or $V_{INH}$
SWITCHING CHARACTERISTICS <sup>4, 5</sup>			
Address to Write Setup Time, $t_{AS}$	0	ns min	
Address to Write Hold Time, $t_{AH}$	0	ns min	
Data Valid to Write Setup Time, $t_{DS}$	50	ns min	
Data Valid to Write Hold Time, $t_{DH}$	0	ns min	
Write Pulsewidth, $t_{WR}$	50	ns min	

NOTES

<sup>1</sup>Maximum possible reference voltage.

<sup>2</sup>Temperature ranges are as follows:

K Version: -40°C to +85°C

B Version: -40°C to +85°C

<sup>3</sup>Guaranteed by design. Not production tested. <sup>4</sup>Sample Tested at 25°C to ensure compliance.

<sup>5</sup>Switching Characteristics apply for single and dual supply operation.

Specifications subject to change without notice.

## **SINGLE SUPPLY** $(V_{DD} = 15 V \pm 5\%, V_{SS} = AGND = DGND = 0 V; V_{REF} = 10 V^1$ unless otherwise noted. All specifications T<sub>MIN</sub> to T<sub>MAX</sub> unless otherwise noted.)

Parameter	K, B Versions <sup>2</sup>	Unit	Conditions/Comments
STATIC PERFORMANCE			
Resolution	8	Bits	
Total Unadjusted Error	±2	LSB max	
Differential Nonlinearity	±1	LSB max	Guaranteed Monotonic
REFERENCE INPUT			
Input Resistance	2	$k\Omega$ min	
Input Capacitance <sup>3</sup>	50	pF min	Occurs when each DAC is loaded with all 0s.
	200	pF max	Occurs when each DAC is loaded with all 1s.
DIGITAL INPUTS			
Input High Voltage, V <sub>INH</sub>	2.4	V min	
Input Low Voltage, V <sub>INL</sub>	0.8	V max	
Input Leakage Current	±1	μA max	$V_{IN} = 0 V \text{ or } V_{DD}$
Input Capacitance	8	pF max	
Input Coding	Binary		
DYNAMIC PERFORMANCE			
Voltage Output Slew Rate <sup>4</sup>	2	V/µs min	
Voltage Output Settling Time <sup>4</sup>	4	us max	Settling Time to $\pm 1/2$ LSB
Digital Crosstalk	10	nV secs typ	
Minimum Load Resistance	2	kΩ min	$V_{OUT}$ = +10 V
POWER SUPPLIES			
V <sub>DD</sub> Range	14.25/15.75	V min/V max	For Specified Performance
I <sub>DD</sub>	13	mA max	Outputs Unloaded; $V_{IN} = V_{INL}$ or $V_{INH}$

NOTES

<sup>1</sup>Maximum possible reference voltage.

<sup>2</sup>Temperature ranges are as follows:

K Version: -40°C to +85°C

B Version: -40°C to +85°C

<sup>3</sup>Guaranteed by design. Not production tested.

<sup>4</sup>Sample Tested at 25°C to ensure compliance.

Specifications subject to change without notice.

### **ORDERING GUIDE**

Model	Temperature Range	Total <sup>1</sup> Unadjusted Error	Package Option <sup>2</sup>
AD7226KN AD7226KP AD7226KR AD7226BQ AD7226BRS	-40°C to +85°C -40°C to +85°C -40°C to +85°C -40°C to +85°C -40°C to +85°C -40°C to +85°C	±1 LSB ±1 LSB ±1 LSB ±1 LSB ±1 LSB	N-20 P-20A RW-20 Q-20 RS-20

NOTES

<sup>1</sup>Dual-Supply Operation

<sup>2</sup>N = Plastic DIP; P = Plastic Leaded Chip Carrier; Q = CERDIP; RW = SOIC; RS = SSOP

### ABSOLUTE MAXIMUM RATINGS<sup>1</sup>

V <sub>DD</sub> to AGND
V <sub>DD</sub> to DGND
$V_{SS}$ to AGND
$V_{SS}$ to DGND
$V_{DD}$ to $V_{SS}$
AGND to DGND0.3 V, V <sub>DD</sub>
Digital Input Voltage to DGND $\dots -0.3 \text{ V}, \text{ V}_{\text{DD}} + 0.3 \text{ V}$
$V_{REF}$ to AGND0.3 V, $V_{DD}$
$V_{OUT}$ to AGND <sup>2</sup> $V_{SS}$ , $V_{DD}$
Power Dissipation (Any Package) to 75°C500 mW
Derates above 75°C by 2.0 mW/°C
Operating Temperature
Commercial (K Version) $\dots -40^{\circ}$ C to $+85^{\circ}$ C
Industrial (B Version) $\dots -40^{\circ}$ C to $+85^{\circ}$ C
Storage Temperature65°C to +150°C
Lead Temperature (Soldering, 10 secs) 300°C
NOTES

<sup>1</sup>Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only, functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

<sup>2</sup>Outputs may be shorted to AGND provided that the power dissipation of the package is not exceeded. Typically short circuit current to AGND is 50 mA.


#### CAUTION \_


ESD (electrostatic discharge) sensitive device. Electrostatic charges as high as 4000 V readily accumulate on the human body and test equipment and can discharge without detection. Although the AD7226 features proprietary ESD protection circuitry, permanent damage may occur on devices subjected to high energy electrostatic discharges. Therefore, proper ESD precautions are recommended to avoid performance degradation or loss of functionality.



### PIN CONFIGURATIONS

#### **DIP and SOIC/SSOP**





#### TERMINOLOGY

### TOTAL UNADJUSTED ERROR

This is a comprehensive specification that includes full-scale error, relative accuracy and zero code error. Maximum output voltage is  $V_{REF} - 1$  LSB (ideal), where 1 LSB (ideal) is  $V_{REF}/256$ . The LSB size will vary over the  $V_{REF}$  range. Hence the zero code error will, relative to the LSB size, increase as  $V_{REF}$  decreases. Accordingly, the total unadjusted error, which includes the zero code error, will also vary in terms of LSB's over the  $V_{REF}$  range. As a result, total unadjusted error is specified for a fixed reference voltage of 10 V.

#### **RELATIVE ACCURACY**

Relative Accuracy or endpoint nonlinearity, is a measure of the maximum deviation from a straight line passing through the endpoints of the DAC transfer function. It is measured after allowing for zero and full-scale error and is normally expressed in LSB's or as a percentage of full-scale reading.

#### DIFFERENTIAL NONLINEARITY

Differential Nonlinearity is the difference between the measured change and the ideal 1 LSB change between any two adjacent codes. A specified differential nonlinearity of  $\pm 1$  LSB max over the operating temperature range ensures monotonicity.

#### DIGITAL CROSSTALK

The glitch impulse transferred to the output of one converter due to a change in the digital input code to another of the converters. It is specified in nV secs and is measured at  $V_{REF} = 0$  V.

### FULL SCALE ERROR


Full-Scale Error is defined as:

Measured Value - Zero Code Error - Ideal Value

# CIRCUIT INFORMATION D/A SECTION

The AD7226 contains four identical, 8-bit, voltage mode digital-toanalog converters. The output voltages from the converters have the same polarity as the reference voltage allowing single supply operation. A novel DAC switch pair arrangement on the AD7226 allows a reference voltage range from 2 V to 12.5 V.

Each DAC consists of a highly stable, thin-film, R-2R ladder and eight high speed NMOS, single-pole, double-throw switches. The simplified circuit diagram for one channel is shown in Figure 1. Note that  $V_{REF}$  (Pin 4) and AGND (Pin 5) are common to all four DACs.



### INTERFACE LOGIC INFORMATION

Address lines A0 and A1 select which DAC will accept data from the input port. Table I shows the selection table for the four DACs with Figure 4 showing the input control logic. When the  $\overline{WR}$  signal is LOW, the input latches of the selected DAC are transparent and its output responds to activity on the data bus. The data is latched into the addressed DAC latch on the rising edge of  $\overline{WR}$ . While  $\overline{WR}$  is high the analog outputs remain at the value corresponding to the data held in their respective latches.

Table I. AD7226 Truth Table

<b>AD</b> 722 WR	6 Control A1	Inputs A0	AD7226 Operation
Н	Х	Х	No Operation Device Not Selected
L	L	L	DAC A Transparent
£	L	L	DAC A Latched
L	L	Н	DAC B Transparent
£	L	Η	DAC B Latched
L	Η	L	DAC C Transparent
1	Н	L	DAC C Latched
L	Н	Η	DAC D Transparent
ſ	Н	Н	DAC D Latched

L = Low State, H = High State, X = Don't Care





Figure 4. Input Control Logic




3. SELECTED INPUT LATCH IS TRANSPARENT WHILE WR IS LOW, THUS INVALID DATA DURING THIS TIME CAN CAUSE SPURIOUS OUTPUTS.




# **Typical Performance Characteristics–AD7226**


 $(T_A = 25^{\circ}C, V_{DD} = 15 V, V_{SS} = -5 V)$ 




TPC 1. Channel-to-Channel Matching



TPC 2. Relative Accuracy vs. V<sub>REF</sub>



TPC 3. Differential Nonlinearity vs. VREF



TPC 4. Zero Code Error vs. Temperature

### SPECIFICATION RANGES

In order for the DACs to operate to their specifications, the reference voltage must be at least 4 V below the  $V_{DD}$  power supply voltage. This voltage differential is required for correct generation of bias voltages for the DAC switches.

The AD7226 is specified to operate over a V<sub>DD</sub> range from +12 V  $\pm$  5% to +15 V  $\pm$  10% (i.e., from +11.4 V to +16.5 V) with a V<sub>SS</sub> of -5 V  $\pm$  10%. Operation is also specified for a single +15 V  $\pm$  5% V<sub>DD</sub> supply. Applying a V<sub>SS</sub> of -5 V results in improved zero code error, improved output sink capability with outputs near AGND and improved negative-going settling time.

Performance is specified over a wide range of reference voltages from 2 V to  $(V_{DD} - 4 V)$  with dual supplies. This allows a range of standard reference generators to be used such as the AD780, a 2.5 V band gap reference and the AD584, a precision 10 V reference. Note that in order to achieve an output voltage range of 0 V to 10 V a nominal 15 V  $\pm$  5% power supply voltage is required by the AD7226.

### SETTLING TIME

The output stage of the buffer amplifiers consists of a bipolar NPN transistor from the  $V_{\rm DD}$  line and a constant current load to  $V_{SS}.V_{SS}$  is the negative power supply for the output buffer amplifiers. As mentioned in the op amp section, in single supply operation the NMOS transistor will come out of saturation as the output voltage approaches AGND and will act as a resistive load of approximately 2 k $\Omega$  to AGND. As a result, the settling time for negative-going signals approaching AGND in single supply operation will be longer than for dual supply operation where the current load of 400  $\mu$ A is maintained all the way down to AGND. Positive-going settling-time is not affected by  $V_{SS}$ .

The settling-time for the AD7226 is limited by the slew-rate of the output buffer amplifiers. This can be seen from Figure 6 which shows the dynamic response for the AD7226 for a full scale change. Figures 7a and 7b show expanded settling-time photographs with the output waveforms derived from a differential input to an oscilloscope. Figure 7a shows the settling time for a positive-going step and Figure 7b shows the settling time for a negative-going output step.




Figure 6. Dynamic Response ( $V_{SS} = -5 V$ )




Figure 7a. Positive Step Settling Time ( $V_{SS} = -5 V$ )




Figure 7b. Negative Step Settling Time ( $V_{SS} = -5 V$ )

### **GROUND MANAGEMENT**

AC or transient voltages between AGND and DGND can cause noise at the analog output. This is especially true in microprocessor systems where digital noise is prevalent. The simplest method of ensuring that voltages at AGND and DGND are equal is to tie AGND and DGND together at the AD7226. In more complex systems where the AGND and DGND intertie is on the backplane, it is recommended that two diodes be connected in inverse parallel between the AD7226 AGND and DGND pins (IN914 or equivalent).

### **Unipolar Output Operation**

This is the basic mode of operation for each channel of the AD7226, with the output voltage having the same positive polarity as +V<sub>REF</sub>. The AD7226 can be operated single supply (V<sub>SS</sub> = AGND) or with positive/negative supplies (see op amp section which outlines the advantages of having negative V<sub>SS</sub>). The code table for unipolar output operation is shown in Table II. Note that the voltage at V<sub>REF</sub> must never be negative with respect to DGND in order to prevent parasitic transistor turn-on. Connections for the unipolar output operation are shown in Figure 8.




Figure 8. AD7226 Unipolar Output Circuit

DAC Latch		
MSB	LSB	Analog Output
1111	1111	$+V_{REF}\left(rac{255}{256} ight)$
1000	0001	$+V_{REF}\left(rac{129}{256} ight)$
1000	0000	$+V_{REF}\left(\frac{128}{256}\right) = +\frac{V_{REF}}{2}$
0111	1111	$+V_{REF}\left(rac{127}{256} ight)$
0000	0001	$+V_{REF}\left(rac{1}{256} ight)$
0000	0000	0 V
	$(11)^{(a-8)}$	. (1)

#### Table II. Unipolar Code Table

Note: 
$$LSB = (V_{REF})(2^{-8}) = V_{REF} \left(\frac{1}{256}\right)$$

### **Bipolar Output Operation**

Each of the DACs of the AD7226 can be individually configured to provide bipolar output operation. This is possible using one external amplifier and two resistors per channel. Figure 9 shows a circuit used to implement offset binary coding (bipolar operation) with DAC A of the AD7226. In this case

$$V_{OUT} = \left(1 + \frac{R^2}{R^1}\right) \times \left(D_A V_{REF}\right) - \left(\frac{R^2}{R^1}\right) \times \left(V_{REF}\right)$$
(3)

With R1 = R2

$$V_{OUT} = (2D_A - 1) \times V_{REF} \tag{4}$$

where  $D_A$  is a fractional representation of the digital word in latch A.

Mismatch between R1 and R2 causes gain and offset errors and therefore these resistors must match and track over temperature. Once again the AD7226 can be operated in single supply or from positive/negative supplies. Table III shows the digital code versus output voltage relationship for the circuit of Figure 9 with R1 = R2.




Figure 9. AD7226 Bipolar Output Circuit

Table III. Bipola	(Offset Binary)	Code Table
-------------------	-----------------	------------

DAC Latch MSB	Contents LSB	Analog Output
1111	1111	$+V_{REF}\left(\frac{127}{128}\right)$
1000	0001	$+V_{REF}\left(\frac{1}{128}\right)$
1000	0000	0 V
0111	1111	$-V_{REF}\left(rac{1}{128} ight)$
0000	0001	$-V_{REF}\left(rac{127}{128} ight)$
0000	0000	$-V_{REF}\left(\frac{128}{128}\right) = -V_{REF}$


#### AGND BIAS

(2)

The AD7226 AGND pin can be biased above system GND (AD7226 DGND) to provide an offset "zero" analog output voltage level. Figure 10 shows a circuit configuration to achieve this for channel A of the AD7226. The output voltage,  $V_{OUT}A$ , can be expressed as:

$$V_{OUT}A = V_{BLAS} + D_A(V_{IN}) \tag{5}$$

where  $D_A$  is a fractional representation of the digital input word  $(0 \le D \le 255/256)$ .



### STAIRCASE WINDOW COMPARATOR

In many test systems, it is important to be able to determine whether some parameter lies within defined limits. The staircase window comparator of Figure 14a is a circuit that can be used, for example, to measure the  $V_{OH}$  and  $V_{OL}$  thresholds of a TTL device under test. Upper and lower limits on both  $V_{OH}$  and  $V_{OL}$  can be programmably set using the AD7226. Each adjacent pair of comparators forms a window of programmable size. If  $V_{TEST}$  lies within a window, then the output for that window will be high. With a reference of 2.56 V applied to the  $V_{REF}$  input, the minimum window size is 10 mV.






Figure 14a. Logic Level Measurement





The circuit can easily be adapted to allow for overlapping of windows as shown in Figure 15a. If the three outputs from this circuit are decoded then five different nonoverlapping programmable windows can again be defined.




Figure 15a. Overlapping Windows




Figure 15b. Window Structure




Figure 16. Varying Reference Signal

### VARYING REFERENCE SIGNAL

In some applications, it may be desirable to have a varying signal applied to the reference input of the AD7226. The AD7226 has multiplying capability within upper and lower limits of reference voltage when operated with dual supplies. The upper and lower limits are those required by the AD7226 to achieve its linearity specification. Figure 16 shows a sine wave signal applied to the reference input of the AD7226. For input signal frequencies up to 50 kHz, the output distortion typically remains less than 0.1%. Typical 3 dB bandwidth figure is 700 kHz.

### **OFFSET ADJUST**

Figure 17 shows how the AD7226 can be used to provide programmable input offset voltage adjustment for the AD544 op amp. Each output of the AD7226 can be used to trim the input offset voltage on one AD544. The 620 k $\Omega$  resistor tied to 10 V provides a fixed bias current to one offset node. For symmetrical adjustment, this bias current should equal the current in the other offset node with the half-full scale code (i.e., 10000000) on the DAC. Changing the code on the DAC varies the bias current and hence provides offset adjust for the AD544. For example, the input offset voltage on the AD544J, which has a maximum of ±2 mV, can be programmably trimmed to ±10  $\mu$ V.




Figure 17. Offset Adjust for AD544




Figure 18. AD7226 to 8085A Interface




Figure 19. AD7226 to 6809 Interface




Figure 20. AD7226 to 6502 Interface





Figure 21. AD7226 to Z-80 Interface

## 20-Lead Plastic Dual In-Line Package [PDIP]

(N-20)

Dimensions shown in inches and (millimeters)



20-Lead Ceramic Dual In-Line Package [CERDIP] (Q-20) c (

Dimensions shown in inches and )millimeters

### **OUTLINE DIMENSIONS**

### 20-Lead Standard Small Outline Package [SOIC] Wide Body


(RW-20) Dimensions shown in millimeters and (inches)

13.00 (0.5118) 12.60 (0.4961) H Ħ H 7.60 (0.2992) 7.40 (0.2913) 10.65 (0.4193) 10.00 (0.3937) 10 Η Η Η Н H 2.65 (0.1043) 0.75 (0.0295) 0.25 (0.0098) × 45° 2.35 (0.0925) 0.30 (0.0118) 0.10 (0.0039) ¥ 0.51 (0.0201) SEATING 0.33 (0.0130) PLANE 8 1.27 1.27 (0.0500) COPLANARITY 0.32 (0.0126) (0.0500) BSC 0.33 (0.0130) 0.10 0.40 (0.0157) 0.23 (0.0091)



20-Lead Plastic Leaded Chip Carrier [PLCC] (P-20A)

Dimensions shown in inches and (millimeters)



COMPLIANT TO JEDEC STANDARDS MO-047AA CONTROLLING DIMENSIONS ARE IN INCHES; MILLIMETER DIMENSIONS (IN PARENTHESES) ARE ROUNDED-OFF INCH EQUIVALENTS FOR REFERENCE ONLY AND ARE NOT APPROPRIATE FOR USE IN DESIGN

# **Revision History**

Location	Page
3/03—Data Sheet changed from REV. B to REV. C.	
Title Revision	1
3/03—Data Sheet changed from REV. A to REV. B.	
Edits to FEATURES	1
Edits to SPECIFICATIONS	2
Edits to ORDERING GUIDE	3
Edits to ABSOLUTE MAXIMUM RATINGS	3
Edits to PIN CONFIGURATIONS	4
Edits to SPECIFICATIONS RANGES	8
OUTLINE DIMENSIONS updated	13
RS-20 package added	13
Updated RS-20 package OUTLINE DIMENSIONS	13

C00987-0-3/03(C)