### MAX86160 Evaluation Kit

### **General Description**

The MAX86160 evaluation kit (MAX86160EVSYS#) provides a proven design to evaluate the MAX86160 integrated heart-rate monitor sensor module. The EV kit consist of two boards. IFC6410 is the main board and MAX86160 Breakout EV kit is the daughter board that includes the MAX86160. The EV kit is powered using an external 5V/3A power supply to the IFC6410, and +1.8V through an LDO for the sensor and +5.0V for the internal LEDs of the MAX86160.

The EV kit comes with a MAX86160EFN+ installed in an 18-pin OLGA package.

### **Features**

- Real-Time Monitoring
- Data-Logging Capabilities
- · Fully Assembled and Tested
- Windows® 7, and Windows 8/8.1-Compatible Software

Ordering Information appears at end of data sheet.

Windows is a registered trademark and registered service mark of Microsoft Corporation.

### **Quick Start**

 MAX86160 EV Kit (MAX86160 Breakout EV kit, IFC6410, 5V/3A power adapter and micro-USB cable included)

**Evaluates: MAX86160** 

Windows PC

#### **Procedure**

The EV kit is fully assembled and tested. Follow the steps below to verify board operation:

- Visit <u>www.maximintegrated.com/evkit-software</u> to download the most recent version of the EV kit software, SetupPPG\_EvKit\_max86160\_x.x.zip. Save the EV kit software to a temporary folder and uncompress the ZIP file.
- 2) Open SetupPPG\_EvKit\_max86160\_x.x.msi and follow the instructions from the pop-up windows as shown in Figure 1, Figure 2, and Figure 3.
- Connect the MAX86160 Breakout EV Kit (J4 and J5) to IFC6410 main board (P1 and P3), as shown in Figure 4.
- 4) Power up the boards by connecting the 5V/3A power supply adapter to the IFC6410 (J4) and wall socket.
- 5) Connect the micro-USB cable from the PC to the EV kit board through J3.
- 6) Install the ADB drivers for IFC6410. Drivers can be found in the installed folder of Maxim SensorStudio, ...\Maxim Integrated\SensorStudio5\USB drivers
- 7) Open SensorStudio5 and verify that the EV kit is connected by observing the status bar at the lower-left corner of the GUI, as shown in <a href="Figure 5">Figure 5</a>. If "Disconnected" is shown, please double-check the board's power supply, USB connection, and press "Refresh" to try.
- 8) From the top menu, choose **View** and then click on "PPG\_EvKit". The MAX86160 PPG evaluation page will then appear, as shown in Figure 6.
- Pressing the Start Monitoring button with the AGC box checked will start the PPG evaluation. LED current will automatically be adjusted by the driver.
- 10) Place the test subject on top of the MAX86160 (U1) of the MAX86160 Breakout EV Kit and observe the PPG graphs. See Figure 7.





Figure 1. Setup SensorStudio Software - Step 1




Figure 2. Setup SensorStudio Software - Step 2





Figure 3. Setup SensorStudio Software - Step 3






Figure 4. Hardware Setup




Figure 5. Maxim SensorStudio GUI




Figure 6. Maxim SensorStudio GUI - PPG Evaluation Page



Figure 7. Maxim SensorStudio GUI - PPG Evaluation Page: Monitoring Data

### **Detailed Description of Software**

The main window of the SensorStudio displays the PPG waveforms (ADC counts over time), Sample Rate settings, pulse width settings and LED currents settings. By default, the AGC (auto-gain control) is enabled, in this mode, the LED currents will be dynamically controlled by the software driver to achieve optimal signal. Under this mode, the sample rate is set to 400hz. In order to manually control the settings menu inside the PPG Settings Tab (sample rate, pulse width and LEDs current), AGC must be unchecked.

### **Data Logging**

The software also provides capability of Data logging. First of all, check the "Log to File" option, and entered the file name by pressing "Browse" (by default under folder \MaximLogs\.). The log file will start saving data once "Start Monitoring" is pressed.

### **PPG Settings**

Within the PPG Settings tab, both the drive current of IR and Green LED can be adjusted individually. Each LED driver is consisted of four different ranges which can be chosen from IR LED Range/Green LED Range

- 0 **51**mA (0.2mA/LSB)
- 0 102mA (0.4mA/LSB)
- 0 153mA (0.6mA/LSB)
- 0 204mA (0.8mA/LSB)

After the range is chosen, the LED current can be adjusted from the IR and Green LED current, respectively.

In addition to the LED Currents, the PPG Settings Tab also consists of controls to the sample rate and pulse width. For more information about the parameters, please refer to the sensor data sheet.

The **Sample Rate** drop-down list is adjustable from 10Hz to 3200Hz.

Evaluates: MAX86160

The **Pulse Width** drop-down list is adjustable from 50Hz to 400µsec.

The **ADC Range** drop-down list is adjustable from 4096 to 32768nA.

### FIFO Settings

**FIFO Almost Full** indicate how many new samples can be written to the FIFO before the interrupt is asserted. For example, if it is set to 15, the interrupt triggers when there is 17 empty space left (15 data samples), and so on.

By Checking "FIFO Rolls on Full" options, the FIFO will automatically roll over when it is full. Otherwise, the FIFO will stops accepting new data until it's read out.

To reduce the amount of data throughput, adjacent samples (in each individual channel) can be averaged and decimated on the chip by setting the Sample Averaging.

The **Sample Averaging** drop-down list is adjustable from 1 to 32.

### RegMapForm

The software also provides capability of viewing and changing the Register Settings of the sensor. This feature can be opened by going to the top menu  $\rightarrow$  View  $\rightarrow$  Register Map, as shown in Figure 8.

The I<sup>2</sup>C register can be read back and written to by using the RegMapForm tool (Figure 9). Double-click on the bitfield you would like to change to flip the bit. Then, click Set Reg to update the settings.

By using the manual update feature, one can also read and set the sensor register settings easily.

www.maximintegrated.com Maxim Integrated | 9




Figure 8. Register Map Options




Figure 9. Register Map User Interface

## **Detailed Description of Hardware**

The MAX86160 EV kit provides a proven design to evaluate the MAX86160 integrated heart-rate monitor sensor module. The EV kit is powered through the +5V/3A from the DC Power Adapter to IFC6410 main board. Then +5V supply from the main board is used for the +VLED supply

and regulated +1.8V to  $V_{DD}$  supply of the MAX86160. The CPU on the IFC6410 communicates with the MAX86160 through interrupt signal and I<sup>2</sup>C interface. There are a lot of different connectors option on the breakout EV kit board, however, only Connector 2 (J4 and J5) will be utilized in this EV kit.

Evaluates: MAX86160

### **Component List**

PART	QTY	DESCRIPTION
Inforce IFC6410	1	EV KIT motherboard
MAX86160EVKIT	1	MAX86160 Breakout EVKIT

## **Ordering Information**

PART	TYPE	
MAX86160EVSYS#	EVKIT	

#Denotes RoHS compliant.

# **Component Information, PCB Layout, and Schematic**

See the following links for component information, PCB layout diagrams, and schematic.

- MAX86160 EV BOM
- MAX86160 EV PCB
- MAX86160 EV Schematic

www.maximintegrated.com Maxim Integrated | 12

# MAX86160 Evaluation Kit

# **Revision History**

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	8/16	Initial release	_

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at www.maximintegrated.com.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time.


TITLE: Bill of Materials DATE: 01/23/2016


DESIGN: max86160\_breakout\_evkit\_p1

ITEM	QTY	REF DES	MAXINV	MFG PART #	MFCTR	VALUE	DESCRIPTION
							CADACITOR, SAAT (0003), CEDANAIC CHIR. 0 1115.
							CAPACITOR; SMT (0603); CERAMIC CHIP; 0.1UF;
١ ,	,	C2, C4, C5	20-000U1-10	C0603C104K8RAC	KEMET	0.1UF	10V; TOL=10%; MODEL=C0603 SERIES; TG=-55 DEGC TO +125 DEGC; TC=X7R
3	3	C2, C4, C5	20-00001-10	CU0U3C1U4K6KAC	KEIVIET	0.101	CAPACITOR; SMT (0603); CERAMIC CHIP; 2.2UF;
		C3, C11,		GRM188R71A225KE15;	MURATA;		10V; TOL=10%; TG=-55 DEGC TO +125 DEGC;
1		C12	20-002U2-10	CL10B225KP8NNN	SAMSUNG	2.2UF	TC=X7R
	,	CIZ	20 00202 10	CLIODZZSKI OIVIVI	SAMSONG	2.201	I C-X/II
							CONNECTOR; MALE; THROUGH HOLE; 68031
11	1	J4	01-68031102H2P-19	68031-102HLF	FCI CONNECT	68031-102HLF	SERIES; BERGSTIK II HEADER; STRAIGHT; 2PINS
						SQW-115-01-L-D-	CONNECTOR; FEMALE; SMT; SQW SERIES;
12	1	J5	01-SQW11501LDVS30P-80	SQW-115-01-L-D-VS	SAMTEC	VS	STRAIGHT; 30PINS
				CRCW06031001FK; ERJ-	VISHAY DALE;		RESISTOR; 0603; 1K; 1%; 100PPM; 0.10W;
14	1	R2	80-0001K-24	3EKF1001V	PANASONIC	1K	THICK FILM
				CRCW06030000ZS;	VISHAY		
				MCR03EZPJ000; ERJ-	DALE/ROHM/		RESISTOR; 0603; 0 OHM; 0%; JUMPER; 0.10W;
15	1	R14	80-0000R-27	3GEY0R00	PANASONIC	0	THICK FILM
							IC; VREG; ULTRA-LOW-NOISE; HIGH PSRR;
17	1	U2	MAX8511EXK18+	MAX8511EXK18+	MAXIM	MAX8511EXK18+	LOW=DROPOUT; LINEAR REGULATOR; SC70-5
20	1		EPCB86160BREAKOUT	MAX86160breakout	MAXIM	PCB	PCB: MAX86160breakout
							EVKIT PART-IC; MAX86160; OLGA18 2.8MM X
							4.3XMM 1.55MM; 0.525MM PITCH; WITH
							A5753-118-23 ALT SYMBOL SOCKET
4		S1	N/A	MAX86160	MAXIM	MAX86160	CONSIDERATION
TOTAL	13						
-							
DO							
NOT							
STUFF							
(DNF)							


		ı	Г	1	1	I	
1		GND, C1_N, C1_P, GPIO, PGND, TP18, +3.3V, ECG_C, ECG_N, ECG_P, LED_DRV2, LED_DRV3	02-TPMINI5005-00	5005	<b>?</b>	5005	TESTPOINT WITH 1.80MM HOLE DIA, RED, COMPACT
							CAPACITOR; SMT (0402); CERAMIC CHIP; 0.1UF;
							25V; TOL=10%; MODEL=GRM SERIES; TG=-55
2	2	C1, C19	20-000U1-B68		MURATA	0.1UF	DEGC TO +125 DEGC; TC=C0G
5	3	C6-C8	20-0001U-63	C0603C105K4RAC; GRM188R71C105KA12; C1608X7R1C105K; EMK107B7105KA	KEMET/MURA TA/TDK/TAIYO YUDEN	1UF	CAPACITOR; SMT (0603); CERAMIC CHIP; 1UF; 16V; TOL=10%; MODEL=; TG=-55 DEGC TO +125 DEGC; TC=X7R
							CAPACITOR; SMT (0603); CERAMIC CHIP; 10UF;
					SAMSUNG		6.3V; TOL=20%; MODEL=CL SERIES; TG=-55
6	1	C9	20-0010U-R1A	CL10B106MQ8NRN	ELECTRONICS	10UF	DEGC TO +125 DEGC; TC=X7R
							CAPACITOR; SMT (0603); CERAMIC CHIP; 10UF;
							10V; TOL=10%; MODEL=; TG=-55 DEGC TO +85
7	1	C20	20-0010U-16	C1608X5R1A106K	TDK	10UF	DEGC; TC=X5R
						SSW-112-22-F-D-	CONNECTOR; FEMALE; SMT; 0.025 POST
8	1	J1	01-SSW11222FDVS24P-17A	SSW-112-22-F-D-VS	SAMTEC	VS	SOCKET; STRAIGHT; 24PINS
							CONNECTOR; FEMALE; THROUGH HOLE; USB
							TYPE C CONNECTOR; RIGHT ANGLE HYBRID;
9	1	J2	01-12401548E42A24P-26	12401548E4#2A	AMPHENOL	12401548E4#2A	24PINS
							CONNECTOR; MALE; SMT; FTSH SERIES; SMT
10	1	13	01-FTSH11701LDH34P-19	FTSH-117-01-L-DH	SAMTEC	FTSH-117-01-L-DH	MICRO HEADER; RIGHT ANGLE; 34PINS
							RESISTOR, 0402, 470 OHM, 1%, 100PPM,
13		R1, R6, R7	80-0470R-23	CRCW0402470RFK	VISHAY DALE	470	0.0625W, THICK FILM
		R10, R11,		CRCW06031001FK; ERJ-	VISHAY DALE;		RESISTOR; 0603; 1K; 1%; 100PPM; 0.10W;
14	4	R16	80-0001K-24	3EKF1001V	PANASONIC	1K	THICK FILM
					ARIES		HT SOCKET; PITCH(0.525MM); NO. OF LEADS-
16	1	U1	03-0.5250LGA18-00	A5753-118-23	ELECTRONICS	A5753-118-23	(18); OLGA 4.30MMX2.80MM
					l		IC; VREG; 500mA LOW-DROPOUT LINEAR
18	1	U3	MAX1818EUT33+	MAX1818EUT33+	MAXIM	MAX1818EUT33+	REGULATOR IN SOT23


					TEXAS		IC; BUF; P82B96 I2C COMPATIBLE DUAL
19	2	U4, U5	10-P82B96PW-U	P82B96PW	INSTRUMENTS	P82B96PW	BIDIRECTIONAL BUS BUFFER; TSSOP8







## TOP SILKSCREEN







# **TOP PASTE**







# **TOP MASK**






TOP







LAYER 2






LAYER 3







# **BOTTOM**







# **BOTTOM MASK**






# **BOTTOM PASTE**






# **BOTTOM SILKSCREEN**

# MAX86160





# CONNECTOR 2

