

421A

LIQUID TIN

Safety Data Sheet

Section 1: Identification

Product Identifier and Other Means of Identification

Product Name: 421A**Other Means of Identification:** Liquid Tin**Related Part #** 421A-125ML, 421A-500ML

Recommended Use and Restriction on Use

Use: Electroless tin plating solution**Uses Advised Against:** Not available

Details of Manufacturer or Importer

ManufacturerMG Chemicals
1210 Corporate Drive
Burlington, Ontario L7L 5R6
CANADAMG Chemicals (Head Office)
9347-193 Street
Surrey, British Columbia V4N 4E7
CANADA**☎** +1-800-340-0772**FAX** +1-800-340-0773**E-MAIL** support@mgchemicals.com**WEB** www.mgchemicals.com**☎** +1-905-331-1396**FAX** +1-905-331-2682**E-MAIL** info@mgchemicals.com**E-MAIL** (Competent Person): sds@mgchemicals.com

Emergency Phone Number

For hazardous material incidents ONLY (leaks, spills, fires, exposures or accidents)USA or CANADA—Call Verisk 3E at **+1-866-519-4752** or **+1-760-476-3962**

(Service access code: 335388)




For emergencies involving the transport of dangerous goods; 24/7 serviceCANADA—Call CANUTEC collect at **+1-613-996-6666** or ***666** on cellular phones

421A
LIQUID TIN
Section 2: Hazards Identification
Classification of Hazardous Chemical
GHS Categories

Criteria	Category	Signal Word	Pictograms
Eye Damage	1	Danger	Corrosion
Skin Corrosion	1	Danger	Corrosion
Reproductive Toxicity	2	Warning	Health
Carcinogenicity	2	Warning	Health
Sensitization Skin	1	Warning	Exclamation
Hazardous to the Aquatic Environment Chronic	3	none	none

Note: The degree of severity is ranked within each hazard class from 1 (Highest Severity) to up to 5 (Lowest Severity), which is opposite to HMIS and NFPA conventions. Severity category rankings do not allow comparisons between classes.

Label Elements

Signal Word	DANGER
Pictograms	Hazard Statements
	H314: Causes severe skin burns and eye damage
	H361: Suspected of damaging fertility or the unborn child if swallowed H351: Suspected of causing cancer if swallowed
	H317: May cause an allergic skin reaction

Section continued on the next page

421A
LIQUID TIN
Continued...

Pictograms	Hazard Statements
<i>No symbol mandatory</i>	H412: Harmful to aquatic life with long lasting effects
Prevention	Precautionary Statements
P102	Keep out of reach of children.
P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P260	Do not breathe vapor, spray, and mists.
P280	Wear protective gloves, protective clothing, and eye protection.
P264	Wash hands thoroughly after handling.
P272	Contaminated work clothing should not be allowed out of the workplace.
P273	Avoid release to the environment.
Response	Precautionary Statements
P310	For all routes of exposure: Immediately call a POISION CENTER or doctor.
P308 + P313	IF exposed or concerned: Get medical advice or attention.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P303 + P361 + 352	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Wash with plenty of water or shower.
P333 + P313	If skin irritation or rash occurs: Get medical advice or attention.
P363	Wash contaminated clothing before reuse.
P301 + P330 + P331	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P304 + P340	IF INHALED: Remove person to fresh air keep comfortable for breathing.
Storage	Precautionary Statements
P405	Store locked up.

Section continued on the next page

421A
LIQUID TIN

Disposal	Precautionary Statements
P501	Dispose of contents in accordance to local, regional, national, and international regulations.

Hazards Not Otherwise Specified

Other Criteria	Hazard Statements/Precautionary Statement	Signal Word	Pictograms
None	None	None	None

Section 3: Composition/Information on Ingredients

CAS #	Chemical Name	%(weight)
62-56-6	thiourea	10%
53408-94-9	tin(II) methanesulphonate	5%
75-75-2	methanesulphonic acid	4%

Note: aqueous solution

Section 4: First-Aid Measures

<i>Exposure Condition</i>	<i>GHS Code/Symptoms/Precautionary Statements</i>
IF IN EYES	P305 + P351 + P338, P310
Immediate Symptoms	<i>redness, pain, severe irritation, burns</i>
Response	Rinse cautiously with water for at least 30 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTRE or doctor.
IF ON SKIN (or hair)	P303 + P361 + P352, P310, P333 + P313, P363
Immediate Symptoms	<i>redness, rash, serious irritation, burns, pain, blisters</i>
Response	Take off immediately contaminated clothing. Wash with plenty of water or shower. Immediately call a POISON CENTRE or doctor. If skin irritation or rash occurs: Get medical attention. Wash contaminated clothing before reuse.

Section continued on the next page

421A**LIQUID TIN***Continued...*

IF INHALED	P304 + P340, P310, P333 + P313
Immediate Symptoms	<i>cough, irritation of the respiratory track, burning sensation in throat, nose and chest</i>
Response	Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTRE or doctor. If exposed or concerned: Get medical attention.
IF SWALLOWED	P301 + P330 + P331, P310, P308 + P313
Immediate Symptoms	<i>burns and burning sensation in mouth, throat, esophagus and stomach</i>
Response	Rinse mouth. Do NOT induce vomiting. Immediately call a POISON CENTRE or doctor. If exposed or concerned: Get medical attention.

Section 5: Fire Fighting Measures

Extinguishing Media	In case of fire: Use extinguish media suitable for surrounding.
Specific Hazards	Will not burn. In a fire, this product can release toxic fumes and gases.
Combustion Products	Produces CO and CO ₂ , nitrogen, tin oxides (SnO _x), sulfur oxides (SO _x)
Fire-Fighter	Wear self-contained breathing apparatus and full fire-fighting turn-out gear.

421A

LIQUID TIN

Section 6: Accidental Release Measures

Personal Protection	Use personal protection recommended in Section 8.
Precautions for Response	Do not breathe mist, spray, vapors. Ensure adequate ventilation. Remove all sources of extreme heat.
Environmental Precautions	Prevent spill from entering drains and waterways.
Containment Methods	Contain with inert absorbent (such as soil, sand, vermiculite).
Cleaning Methods	Sprinkle inert absorbent compound (sand, diatomite, acid binders, universal binders) onto spill, then sweep into a corrosion resistant (plastic) waste container. Wash spill area with soap and water to remove the last traces of residue.
Disposal Methods	Dispose of spill waste according to Section 13.

Section 7: Handling and Storage

Prevention	Keep out of reach of children. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not get in eye, on skin, or on clothing. Do not breathe vapor, spray, and mists. Contaminated work clothing should not be allowed out of the workplace.
Handling	Wear protective gloves, protective clothing, and eye protection. Take off immediately all contaminated clothing and wash them before reuse. Wash hands thoroughly after handling.
Storage	Store locked up. DO NOT FREEZE. Store in a clean and dry area between 5 to 35 °C.

421A
LIQUID TIN
Section 8: Exposure Controls/Personal Protection
Substances with Occupational Exposure Limit Values

Chemical Name	Country	Long Term Exposure Limits (PEL)	Short Term Exposure Limits (STEL)
tin and its inorganic compounds:	ACGIH	2 mg/m ³	Not established
	U.S.A. OSHA PEL	2 mg/m ³	Not established
	Canada AB	2 mg/m ³	Not established
	Canada BC	2 mg/m ³	Not established
	Canada ON	2 mg/m ³	Not established
	Canada QC	2 mg/m ³	Not established

Note: Ingredients are listed in descending weight contribution order (from greatest to least). The ACGIH¹, OSHA (Table Z-1), and Canadian provinces exposure limits were consulted. Limits from the RTECS² database and from suppliers' SDS were also consulted. Short term exposure limits (STEL) are for 15 min and long term permissible exposure limits (PEL) for 8 h.

Engineering Controls

Ventilation Keep airborne concentrations below occupational exposure limits (OEL).

Personal Protective Equipment

Eye protection Wear appropriate protective eyeglasses or chemical safety goggles.

RECOMMENDATION: Ensure that glasses have side shields for lateral protection.

Skin Protection For likely contacts, use of protective gloves in butyl rubber, chloroprene, latex, or other chemically resistant gloves with a minimum thickness of 0.6 mm.

For incidental contacts, use disposable nitrile with a minimum thickness \geq 0.1 mm, or other chemically resistant gloves.

Section continued on the next page

421A
LIQUID TIN

Respiratory Protection For over-exposures up to 10 x OEL of mist, vapors, and spray; wear respirator such as a half-mask respirator with organic vapor cartridges.

RECOMMENDATION: Consult your local safety supply store to ensure that your respirator has a NIOSH (U.S.) approved filter cartridges appropriate for the ingredients listed in Section 3. The respirator should be fitted to the employee by a professional. Ensure vapor cartridges are stored in sealed plastic bags when not being used.

General Hygiene Considerations

Wash hands thoroughly with water and soap after handling.

Section 9: Physical and Chemical Properties

Physical State	Liquid	Lower Flammability Limit	Not available
Appearance	Yellow	Upper Flammability Limit	Not available
Odor	Slight sulfur	Vapor Pressure @20 °C	Not available
Odor Threshold	Not available	Vapor Density	Not available
pH	<1	Relative Density @25 °C	1.25
Freezing/Melting Point	Not available	Solubility in Water	Completely Soluble
Initial Boiling Point	Not available	Partition Coefficient octanol/water	Not available
Flash Point	Not available	Auto-ignition Temperature	Not available
Evaporation Rate	Not available	Decomposition Temperature	Not available
Flammability	Non Flammable	Viscosity @40 °C	<20.5 mm ² /s

421A

LIQUID TIN

Section 10: Stability and Reactivity

Reactivity	Not applicable
Chemical Stability	Chemically stable at normal temperatures and pressures
Conditions to Avoid	Avoid aerosolization and incompatible substances.
Incompatibilities	Avoid strong acids, bases, oxidizers and cyanides.
Polymerization	Will not occur
Decomposition	Will not decompose under normal conditions. For thermal decomposition, see combustion products in Section 5.

Section 11: Toxicological Information**Summary of Effects and Symptoms by Routes of Exposure**

Eyes	Cause redness, pain, severe irritation, or burns. The symptoms may be delayed.
Skin	May causes redness, rash, pain, blisters, serious irritation, or burns. The symptoms may be delayed.
Inhalation	May cause cough, upper respiratory tract irritation, burning sensations (nose, throat, and lung).
Ingestion	May cause burns and burning sensation in mouth, throat, esophagus and stomach.
Chronic	Prolonged and repeated exposure may lead to skin sensitization. Ingestion or inhalation may have reproductive, developmental, and carcinogenic effects.

Section continued on the next page

421A
LIQUID TIN
Acute Toxicity (Lethal Exposure Concentrations)

Chemical Name	LD50 oral	LD50 dermal	LC50 inhalation
thiourea	>2 000 mg/kg Rat	2 800 mg/kg Rabbit	195 mg/L 4 h Rat
tin(II) methanesulphonate	1 621 mg/kg Rat	>2 000 mg/kg Rat	Not available
methanesulphonic acid	>860 mg/kg Rat	>1 000 mg/kg Rabbit	>2 mg/m ³ 1 h Mouse

Note: Toxicity data from the RTECS² and ECHA databases were consulted. The data from supplier SDSs were also consulted.

Other Toxicological Effects

Skin corrosion/irritation	Causes severe skin burns.
Serious eye damage/irritation	Causes serious eye damage.
Sensitization (allergic reactions)	Tin(II) methanesulphonate is a known skin sensitizer.
Carcinogenicity (risk of cancer)	<p>Thiourea is classified as a possible carcinogen based on animal studies and North American regulatory guidelines.</p> <p>Thiourea [CAS# 62-56-6]</p> <p>IARC Group 2B: Possibly carcinogenic to humans</p> <p>ACGIH A3: Confirmed Animal Carcinogen with Unknown Relevance to Humans</p> <p>CA Prop 65: Listed as Carcinogen</p> <p>NTP: Reasonably anticipated to be a human carcinogen</p>
Mutagenicity (risk of heritable genetic effects)	Based on available data, the classification criteria are not met.
Reproductive Toxicity (risk to sex functions)	Thiourea is believed to decrease fertility in males and females based on animal studies.
Teratogenicity (risk of fetus malformation)	Thiourea may present developmental hazard based on animal studies.
STOT-single exposure	Based on available data, the classification criteria are not met.

Section continued on the next page

421A**LIQUID TIN**

STOT-repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met. This product doesn't contain any Cat 1 ingredients.

Section 12: Ecological Information

Ecological classifications are based on the IMDG/GHS criteria in conjunction with ecotoxicological data from our suppliers, the European Chemical Agency database (<http://echa.europa.eu>), and other reliable sources.

Thiourea is an acute category 2 environmental toxicant. It is rapidly biodegradable with minimal LC50 of 10 mg/L 96 h for *Danio rerio* (zebra fish); EC50 of ≥ 5.6 mg/L 48 h *Daphnia magna* (water flea); EC50 of 6.8 mg/L 96 h *Desmodesmus subspicatus* (green algae).

Tin(II) methanesulphonate is a chronic category 2 environmental toxicant.

Based on available data, methanesulphonic acid is not classified as an environmental hazard according to GHS criteria.

Acute Ecotoxicity

See the chronic section.

Chronic Ecotoxicity

Category 3

Harmful to aquatic life with long lasting effects

Avoid release to the environment.

Biodegradability

Not available

Other Effects

Not available

Section 13: Disposal Considerations

Dispose of contents in accordance with all local, regional, national, and international regulations.

421A

LIQUID TIN


Section 14: Transport Information

Ground

Refer to TDG regulations (Canadian Transportation of Dangerous Goods regulations);
USA DOT 49 CFR (Parts 100 to 185) **Regulations.**

Sizes 1 L and under
421A-125ML, 421A-500ML

Limited Quantity



Temperature sensitive—Keep between 5 °C and 35 °C.

Air

Refer to ICAO-IATA Dangerous Goods Regulations.

Sizes 0.5 L and under
421A-125ML, 421A-500ML

Limited Quantity

Max. Net Qty/Pkg
0.5 L



Packing Instr. Y840

Sizes greater than 0.5 to 1 L

FOR REFERENCE ONLY

UN number: UN1760

Shipping Name:

Corrosive Liquid, N.O.S. (tin(II)
methanesulphonate, methanesulphonic acid)

Class: 8


Packing Group: II

Marine Pollutant: No

Packing Instr. 851 (Max Net Qty: 1 L).

Temperature sensitive—Keep between 5 °C and 35 °C.

Section continued on the next page

421A**LIQUID TIN****Sea****Refer to IMDG regulations.**Sizes 1 L and under
421A-125ML, 421A-500ML
Limited Quantity

Sizes greater than 1 L

FOR REFERENCE ONLY

UN number: UN1760**Shipping Name:**Corrosive Liquid, N.O.S. (tin(II)
methanesulphonate, methanesulphonic acid)**Class:** 8**Packing Group:** II**Marine Pollutant:** No**Temperature sensitive—Keep between 5 °C and 35 °C.****Note: Shipper must be appropriately trained and certified before involvement with the transport of dangerous goods.****Section 15: Regulatory Information****Canada****Domestic Substance List (DSL) / Non-Domestic Substance Lists (NDSL)**

All hazardous ingredients are listed on the DSL/NDSL.


Hazardous Products Act (R.S.C., 1985, c. H-3)

The safety data sheet and label comply with the Hazardous Product Act and WHMIS 2015.

Section continued on the next page

421A**LIQUID TIN****USA****Other Classifications****HMIS[®] RATING**

HEALTH:	* 3
FLAMMABILITY:	0
PHYSICAL HAZARD:	1
PERSONAL PROTECTION:	

NFPA[®] 704 CODES

Approximate HMIS and NFPA Risk Ratings Legend:

0 (Low or none); 1 (Slight); 2 (Moderate); 3 (Serious); 4 (Severe)

CAA (Clean Air Act, USA)

This product does not contain any class 1 ozone depleting substances.

This product does not contain any class 2 ozone depleting substances.

This product does not contain substances that are listed as hazardous air pollutants.

EPCRA (Emergency Planning and Right to Know Act, USA, 40 CFR 372.45)

This product contains thiourea (CAS# 62-56-6; reportable quantity = 10 lb), which is subject to the reporting requirements of section 313 Title III of the SARA of 1986 and 40 CFR part 372.

TSCA (Toxic Substances Control Act of 1976, USA)

All substances are TSCA listed.

California Proposition 65 (Chemicals known to cause cancer or reproductive toxicity).

This product contains thiourea, which is listed as a carcinogen.

Europe**RoHS** (Restriction of Hazardous Substances Directive)

This product does not contain any lead, cadmium, mercury, hexavalent chromium, PBB's, PBDE's, DEHP, BBP, DBP, or DIBP and complies with European RoHS regulations.

WEEE (Waste Electrical and Electronic Equipment Directive)

This product is not a piece of electrical or electronics equipment, and is therefore not governed by this regulation.

421A**LIQUID TIN****Section 16: Other Information**

Prepared by the	Regulatory Affairs Department
Date of Review	27 February 2020
Supersedes	15 October 2019
Reason for Changes:	Update to emergency contact information.

Reference

- 1) ACGIH 2017 TLVs and BEIs: Based on the documentation of the threshold limit values for chemical substances and physical agents & biological exposure indices, American Conference of Governmental of Industrial Hygienist Cincinnati, OH (2017).
- 2) All toxicological data were checked against the RTECS (Registry of Toxic Effects of Chemical Substances®)

Abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists (USA)
EC50	Half maximal effective concentration
EL50	Half maximal effective loading
NOELR	No observable effect loading ratio
GHS	Globally Harmonized System of Classification of Labeling of Chemicals
LC50	Lethal Concentration 50%
LCLo	Lowest published lethal concentration
LD50	Lethal Dose 50%
PEL	Permissible Exposure Limit
STEL	Short-Term Exposure Limit
TCLo	Lowest published toxic concentration
TWA	Time Weighted Average
VOC	Volatile Organic Content

Section continued on the next page

421A**LIQUID TIN**

Technical Queries Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Phone: +1-905-331-1396

Mailing Addresses *Manufacturing & Support*
1210 Corporate Drive
Burlington, Ontario, Canada
L7L 5R6

Head Office
9347-193rd Street
Surrey, British Columbia, Canada
V4N 4E7

Disclaimer This safety data sheet is provided as an information resource only. *M.G. Chemicals, Ltd.* believes the information contained herein is accurate and compiled from reliable sources. It is the responsibility of the user to query and verify any information seeming suspect where doubt on the validity may exist. The buyer assumes all responsibility of using and handling the product in accordance with local, regional, national, and international regulations.